

CY7C1318KV18/CY7C1320KV18

18-Mbit DDR II SRAM Two-Word Burst Architecture

Features

- 18-Mbit density (1M × 18, 512K × 36)
- 333-MHz clock for high bandwidth
- Two-word burst for reducing address bus frequency
- Double data rate (DDR) interfaces (data transferred at 666 MHz) at 333 MHz
- Two input clocks (K and K) for precise DDR timing SRAM uses rising edges only
- Two input clocks for output data (C and C) to minimize clock skew and flight time mismatches
- Echo clocks (CQ and CQ) simplify data capture in high-speed systems
- Synchronous internally self-timed writes
- DDR II operates with 1.5 cycle read latency when DOFF is asserted HIGH
- Operates similar to DDR-I device with 1 cycle read latency when DOFF is asserted LOW
- 1.8 V core power supply with HSTL inputs and outputs
- Variable drive HSTL output buffers
- Expanded HSTL output voltage (1.4 V–V_{DD})

 □ Supports both 1.5 V and 1.8 V I/O supply
- Available in 165-ball FBGA package (13 × 15 × 1.4 mm)
- Offered in both Pb-free and non Pb-free packages
- JTAG 1149.1 compatible test access port
- Phase locked loop (PLL) for accurate data placement

Configurations

CY7C1318KV18 – 1M × 18 CY7C1320KV18 – 512K × 36

Functional Description

The CY7C1318KV18, and CY7C1320KV18 are 1.8 V synchronous pipelined SRAM equipped with DDR II architecture. The DDR II consists of an SRAM core with advanced synchronous peripheral circuitry and a 1-bit burst counter. Addresses for read and write are latched on alternate rising edges of the input (K) clock. Write data is registered on the rising edges of both K and K. Read data is driven on the rising edges of C and C if provided, or on the rising edge of K and K if C/C are not provided. On CY7C1318KV18 and CY7C1320KV18, the burst counter takes in the least significant bit of the external address and bursts two 18-bit words in the case of CY7C1318KV18 and two 36-bit words in the case of CY7C1320KV18 sequentially into or out of the device.

Asynchronous inputs include an output impedance matching input (ZQ). Synchronous data outputs (Q, sharing the same physical pins as the data inputs D) are tightly matched to the two output echo clocks CQ/CQ, eliminating the need for separately capturing data from each individual DDR SRAM in the system design. Output data clocks (C/C) enable maximum system clocking and data synchronization flexibility.

All synchronous inputs pass through input registers controlled by the K or \overline{K} input clocks. All data outputs pass through output registers controlled by the C or \overline{C} (or K or \overline{K} in a single clock domain) input clocks. Writes are conducted with on-chip synchronous self-timed write circuitry.

For a complete list of related documentation, click here.


Selection Guide

Description		333 MHz	300 MHz	250 MHz	Unit
Maximum operating frequency		333	300	250	MHz
Maximum operating current	× 18	450	430	380	mA
	× 36	560	520	460	


Cypress Semiconductor CorporationDocument Number: 001-58905 Rev. *L



Logic Block Diagram - CY7C1318KV18



Logic Block Diagram - CY7C1320KV18





Contents

Pin Configurations	4
Pin Definitions	5
Functional Overview	6
Read Operations	6
Write Operations	
Byte Write Operations	7
Single Clock Mode	7
DDR Operation	7
Depth Expansion	7
Programmable Impedance	7
Echo Clocks	7
PLL	7
Application Example	8
Truth Table	
Burst Address Table	9
Write Cycle Descriptions	10
Write Cycle Descriptions	
IEEE 1149.1 Serial Boundary Scan (JTAG)	
Disabling the JTAG Feature	
Test Access Port	
Performing a TAP Reset	
TAP Registers	
TAP Instruction Set	
TAP Controller State Diagram	
TAP Controller Block Diagram	
TAP Electrical Characteristics	
TAP AC Switching Characteristics	
TAP Timing and Test Conditions	
Identification Register Definitions	
Scan Register Sizes	18

Instruction Codes	_
Boundary Scan Order	
Power Up Sequence in DDR II SRAM	20
Power Up Sequence	20
PLL Constraints	20
Maximum Ratings	21
Operating Range	21
Neutron Soft Error Immunity	21
Electrical Characteristics	
DC Electrical Characteristics	21
AC Electrical Characteristics	23
Capacitance	23
Thermal Resistance	23
AC Test Loads and Waveforms	23
Switching Characteristics	24
Switching Waveforms	26
Read/Write/Deselect Sequence	26
Ordering Information	27
Ordering Code Definitions	27
Package Diagram	28
Acronyms	
Document Conventions	29
Units of Measure	29
Document History Page	30
Sales, Solutions, and Legal Information	32
Worldwide Sales and Design Support	32
Products	32
PSoC® Solutions	32
Cypress Developer Community	
Technical Support	32



Pin Configurations

The pin configurations for CY7C1318KV18, and CY7C1320KV18 follow. [1]

Figure 1. 165-ball FBGA (13 × 15 × 1.4 mm) pinout CY7C1318KV18 (1M × 18)

	1	2	3	4	5	6	7	8	9	10	11
Α	CQ	NC/72M	Α	R/W	BWS ₁	K	NC/144M	LD	Α	NC/36M	CQ
В	NC	DQ9	NC	Α	NC/288M	K	BWS ₀	Α	NC	NC	DQ8
С	NC	NC	NC	V_{SS}	А	A0	Α	V _{SS}	NC	DQ7	NC
D	NC	NC	DQ10	V_{SS}	V_{SS}	V_{SS}	V_{SS}	V _{SS}	NC	NC	NC
E	NC	NC	DQ11	V_{DDQ}	V _{SS}	V _{SS}	V _{SS}	V_{DDQ}	NC	NC	DQ6
F	NC	DQ12	NC	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	NC	DQ5
G	NC	NC	DQ13	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	NC	NC
Н	DOFF	V_{REF}	V_{DDQ}	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	V_{DDQ}	V_{REF}	ZQ
J	NC	NC	NC	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	DQ4	NC
K	NC	NC	DQ14	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	NC	DQ3
L	NC	DQ15	NC	V_{DDQ}	V_{SS}	V_{SS}	V_{SS}	V_{DDQ}	NC	NC	DQ2
М	NC	NC	NC	V_{SS}	V_{SS}	V_{SS}	V_{SS}	V _{SS}	NC	DQ1	NC
N	NC	NC	DQ16	V _{SS}	Α	Α	Α	V _{SS}	NC	NC	NC
Р	NC	NC	DQ17	Α	Α	С	Α	Α	NC	NC	DQ0
R	TDO	TCK	Α	Α	Α	C	Α	Α	Α	TMS	TDI

CY7C1320KV18 (512K × 36)

	1	2	3	4	5	6	7	8	9	10	11
Α	CQ	NC/144M	NC/36M	R/W	BWS ₂	K	BWS ₁	LD	Α	NC/72M	CQ
В	NC	DQ27	DQ18	Α	BWS ₃	K	BWS ₀	Α	NC	NC	DQ8
С	NC	NC	DQ28	V _{SS}	Α	A0	Α	V_{SS}	NC	DQ17	DQ7
D	NC	DQ29	DQ19	V _{SS}	V_{SS}	V_{SS}	V_{SS}	V_{SS}	NC	NC	DQ16
E	NC	NC	DQ20	V_{DDQ}	V_{SS}	V_{SS}	V_{SS}	V_{DDQ}	NC	DQ15	DQ6
F	NC	DQ30	DQ21	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	NC	DQ5
G	NC	DQ31	DQ22	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	NC	DQ14
Н	DOFF	V_{REF}	V_{DDQ}	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	V_{DDQ}	V_{REF}	ZQ
J	NC	NC	DQ32	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	DQ13	DQ4
K	NC	NC	DQ23	V_{DDQ}	V_{DD}	V_{SS}	V_{DD}	V_{DDQ}	NC	DQ12	DQ3
L	NC	DQ33	DQ24	V_{DDQ}	V_{SS}	V_{SS}	V_{SS}	V_{DDQ}	NC	NC	DQ2
М	NC	NC	DQ34	V _{SS}	V_{SS}	V_{SS}	V_{SS}	V_{SS}	NC	DQ11	DQ1
N	NC	DQ35	DQ25	V _{SS}	Α	Α	Α	V _{SS}	NC	NC	DQ10
Р	NC	NC	DQ26	Α	Α	С	Α	Α	NC	DQ9	DQ0
R	TDO	TCK	Α	Α	Α	С	Α	Α	Α	TMS	TDI

Note

Document Number: 001-58905 Rev. *L

^{1.} NC/36M, NC/72M, NC/144M, and NC/288M are not connected to the die and can be tied to any voltage level.



Pin Definitions

Pin Name	I/O	Pin Description
DQ _[x:0]	Input output- synchronous	Data Input Output Signals . Inputs are sampled on the rising edge of K and \overline{K} clocks during valid write operations. These pins drive out the requested data when the read operation is active. Valid data is driven out on the rising edge of both the C and \overline{C} clocks during read operations or K and \overline{K} when in single clock mode. When read access is deselected, $Q_{[x:0]}$ are automatically tristated. CY7C1318KV18 – $DQ_{[17:0]}$ CY7C1320KV18 – $DQ_{[35:0]}$
LD	Input- synchronous	Synchronous Load . This input is brought LOW when a bus cycle sequence is defined. This definition includes address and read/write direction. All transactions operate on a burst of 2 data.
BWS ₀ , BWS ₁ , BWS ₂ , BWS ₃	Input- synchronous	Byte Write Select 0, 1, 2, and 3 – Active LOW. Sampled on the rising edge of the K and \overline{K} clocks during write operations. Used to select which byte is written into the device during the current portion of the write operations. Bytes not written remain unaltered. CY7C1318KV18 – $\overline{BWS_0}$ controls $D_{[8:0]}$ and $\overline{BWS_1}$ controls $D_{[17:9]}$. $\overline{BWS_2}$ controls $D_{[26:18]}$ and $\overline{BWS_3}$ controls $D_{[35:27]}$. All the Byte Write Selects are sampled on the same edge as the data. Deselecting a Byte Write Select ignores the corresponding byte of data and it is not written into the device.
A, A0	Input- synchronous	Address Inputs. These address inputs are multiplexed for both read and write operations. Internally, the device is organized as 1M × 18 (2 arrays each of 512K × 18) for CY7C1318KV18, and 512K × 36 (2 arrays each of 256K × 36) for CY7C1320KV18. CY7C1318KV18 – A0 is the input to the burst counter. These are incremented in a linear fashion internally. 20 address inputs are needed to access the entire memory array. CY7C1320KV18 – A0 is the input to the burst counter. These are incremented in a linear fashion internally. 19 address inputs are needed to access the entire memory array. All the address inputs are ignored when the appropriate port is deselected.
R/W	Input- synchronous	Synchronous Read or Write Input. When LD is LOW, this input designates the access type (read when R/W is HIGH, write when R/W is LOW) for loaded address. R/W must meet the setup and hold times around edge of K.
С	Input clock	Positive Input Clock for Output Data . C is used in conjunction with \overline{C} to clock out the read data from the device. C and \overline{C} can be used together to deskew the flight times of various devices on the board back to the controller. See Application Example on page 8 for further details.
C	Input clock	Negative Input Clock for Output Data . \overline{C} is used in conjunction with C to clock out the read data from the device. C and \overline{C} can be used together to deskew the flight times of various devices on the board back to the controller. See Application Example on page 8 for further details.
K	Input clock	Positive Input Clock Input . The rising edge of K is used to capture synchronous inputs to the device and to drive out data through $Q_{[x:0]}$ when in single clock mode. All accesses are initiated on the rising edge of K.
K	Input clock	Negative Input Clock Input . \overline{K} is used to capture synchronous data being presented to the device and to drive out data through $Q_{[x:0]}$ when in single clock mode.
CQ	Output clock	CQ Referenced with respect to C . This is a free running clock and is synchronized to the input clock for output data (C) of the DDR II. In the single clock mode, CQ is generated with respect to K. The timing for the echo clocks is shown in the Switching Characteristics on page 24.
CQ	Output clock	CQ Referenced with respect to C. This is a free running clock and is synchronized to the input clock for output data (C) of the DDR II. In the single clock mode, CQ is generated with respect to K. The timing for the echo clocks is shown in the Switching Characteristics on page 24.
ZQ	Input	Output Impedance Matching Input. This input is used to tune the device outputs to the system data bus impedance. CQ, CQ, and $Q_{[x:0]}$ output impedance are set to $0.2 \times RQ$, where RQ is a resistor connected between ZQ and ground. Alternatively, this pin can be connected directly to V_{DDQ} , which enables the minimum impedance mode. This pin cannot be connected directly to GND or left unconnected.



Pin Definitions (continued)

Pin Name	I/O	Pin Description
DOFF	Input	PLL Turn Off – Active LOW . Connecting this pin to ground turns off the PLL inside the device. The timing in the PLL turned off operation differs from those listed in this data sheet. For normal operation, this pin is connected to a pull up through a 10 k Ω or less pull up resistor. The device behaves in DDR-I mode when the PLL is turned off. In this mode, the device can be operated at a frequency of up to 167 MHz with DDR-I timing.
TDO	Output	TDO Pin for JTAG.
TCK	Input	TCK Pin for JTAG.
TDI	Input	TDI Pin for JTAG.
TMS	Input	TMS Pin for JTAG.
NC	N/A	Not Connected to the Die. Can be tied to any voltage level.
NC/36M	Input	Not Connected to the Die. Can be tied to any voltage level.
NC/72M	Input	Not Connected to the Die. Can be tied to any voltage level.
NC/144M	Input	Not Connected to the Die. Can be tied to any voltage level.
NC/288M	Input	Not Connected to the Die. Can be tied to any voltage level.
V _{REF}	Input- reference	Reference Voltage Input . Static input used to set the reference level for HSTL inputs, outputs, and AC measurement points.
V_{DD}	Power supply	Power supply inputs to the core of the device.
V_{SS}	Ground	Ground for the device.
V_{DDQ}	Power supply	Power supply inputs for the outputs of the device.

Functional Overview

The CY7C1318KV18, and CY7C1320KV18 are synchronous pipelined burst SRAMs equipped with a DDR interface, which operates with a read latency of one and a half cycles when DOFF pin is tied HIGH. When DOFF pin is set LOW or connected to V_{SS} the device behaves in DDR-I mode with a read latency of one clock cycle.

Accesses are initiated on the rising edge of the positive input clock (K). All synchronous input timing is referenced from the rising edge of the input clocks (K and K) and all output timing is referenced to the rising edge of the output clocks (C/\overline{C} , or K/K when in single clock mode).

All synchronous data inputs $(D_{[x:0]})$ pass through input registers controlled by the rising edge of the input clocks (K and K). All synchronous data outputs $(Q_{[x:0]})$ pass through output_registers controlled by the rising edge of the output clocks (C/\overline{C}) , or K/\overline{K} when in single clock mode).

All synchronous control (R/\overline{W} , \overline{LD} , $\overline{BWS}_{[0:X]}$) inputs pass through input registers controlled by the rising edge of the input clock (K).

CY7C1318KV18 is described in the following sections. The same basic descriptions apply to CY7C1320KV18.

Read Operations

The CY7C1318KV18 is organized internally as a two arrays of $512K \times 18$. Accesses are completed in a burst of two sequential 18-bit data words. Read operations are initiated by asserting R/W HIGH and LD LOW at the rising edge of the positive input clock (K). The address presented to address inputs is stored in the read address register and the least significant bit of the address is presented to the burst counter. The burst counter

increments the address in a linear fashion. Following the next K clock rise, the corresponding 18-bit word of data from this address location is driven onto the $Q_{[17:0]}$ using \overline{C} as the output timing reference. On the subsequent rising edge of C the next 18-bit data word from the address location generated by the burst counter is driven onto the $Q_{[17:0]}$. The requested data is valid $0.\underline{45}$ ns from the rising edge of the output clock (C or \overline{C} , or K and \overline{K} when in single clock mode, 250 MHz, and 300 MHz device). To maintain the internal logic, each read access must be allowed to complete. Read accesses can be initiated on every rising edge of the positive input clock (K).

When read access is deselected, the CY7C1318KV18 first completes the pending read transactions. Synchronous internal circuitry automatically tristates the output following the next rising edge of the positive output clock (C). This enables for a transition between devices without the insertion of wait states in a depth expanded memory.

Write Operations

Write operations are initiated by asserting R/W LOW and $\overline{\text{LD}}$ LOW at the rising edge of the positive input clock (K). The address presented to address inputs is stored in the write address register and the least significant bit of the address is presented to the burst counter. The burst counter increments the address in a linear fashion. On the following K clock rise, the data presented to $D_{[17:0]}$ is latched and stored into the 18-bit write data register, provided $\overline{\text{BWS}}_{[1:0]}$ are both asserted active. On the subsequent rising edge of the Negative Input Clock (K) the information presented to $D_{[17:0]}$ is also stored into the write data register, provided $\overline{\text{BWS}}_{[1:0]}$ are both asserted active. The 36 bits of data are then written into the memory array at the specified location. Write accesses can be initiated on every rising edge of



the positive input clock (K). Doing so pipelines the data flow such that 18 bits of data can be transferred into the device on every rising edge of the input clocks (K and \overline{K}).

When the write access is deselected, the device ignores all inputs after the pending write operations have been completed.

Byte Write Operations

Byte write operations are supported by the CY7C1318KV18. A write operation is initiated as described in the Write Operations section. The bytes that are written are determined by BWS₀ and BWS₁, which are sampled with each set of 18-bit data words. Asserting the appropriate Byte Write Select input during the data portion of a write latches the data being presented and writes it into the device. Deasserting the Byte Write Select input during the data portion of a write enables the data stored in the device for that byte to remain unaltered. This feature is used to simplify read, modify, or write operations to a byte write operation.

Single Clock Mode

The CY7C1318KV18 is used with a single clock that controls both the input and output registers. In this mode, the device recognizes only a single pair of input clocks (K and K) that control both the input and output registers. This operation is identical to the operation if the device had zero skew between the K/K and C/C clocks. All timing parameters remain the same in this mode. To use this mode of operation, the user must tie C and \overline{C} HIGH at power on. This function is a strap option and not alterable during device operation.

DDR Operation

The CY7C1318KV18 enables high-performance operation through high clock frequencies (achieved through pipelining) and DDR mode of operation. The CY7C1318KV18 requires a single No Operation (NOP) cycle during transition from a read to a write cycle. At higher frequencies, some applications may require a second NOP cycle to avoid contention.

If a read occurs after a write cycle, address and data for the write are stored in registers. The write information must be stored because the SRAM cannot perform the last word write to the array without conflicting with the read. The data stays in this register until the next write cycle occurs. On the first write cycle after the read(s), the stored data from the earlier write is written into the SRAM array. This is called a posted write.

If a read is performed on the same address on which a write is performed in the previous cycle, the SRAM reads out the most current data. The SRAM does this by bypassing the memory array and reading the data from the registers.

Depth Expansion

Depth expansion requires replicating the \overline{LD} control signal for each bank. All other control signals can be common between banks as appropriate.

Programmable Impedance

An external resistor, RQ, must be connected between the ZQ pin on the SRAM and V_{SS} to allow the SRAM to adjust its output driver impedance. The value of RQ must be 5 × the value of the intended line impedance driven by the SRAM. The allowable range of RQ to guarantee impedance matching with a tolerance of ±15% is between 175 Ω and 350 Ω , with V_{DDQ} = 1.5 V. The output impedance is adjusted every 1024 cycles upon power up to account for drifts in supply voltage and temperature.

Echo Clocks

Echo clocks are provided on the DDR II to simplify data capture on high speed systems. Two echo clocks are generated by the DDR II. CQ is referenced with respect to C and CQ is referenced with respect to \overline{C} . These are free running clocks and are synchronized to the output clock of the DDR II. In single clock mode, CQ is generated with respect to K and \overline{CQ} is generated with respect to K. The timing for the echo clocks is shown in the Switching Characteristics on page 24.

PLL


These chips use a PLL that is designed to function between 120 MHz and the specified maximum clock frequency. During power up, when the DOFF is tied HIGH, the PLL is locked after 20 μs of stable clock. The PLL can also be reset by slowing or stopping the input clock K and K for a minimum of 30 ns. However, it is not necessary to reset the PLL to lock to the desired frequency. The PLL automatically locks 20 μs after a stable clock is presented. The PLL may be disabled by applying ground to the DOFF pin. When the PLL is turned off, the device behaves in DDR-I mode (with one cycle latency and a longer access time).



Application Example

Figure 2 shows two DDR II used in an application.

Figure 2. Application Example





Truth Table

The truth table for the CY7C1318KV18, and CY7C1320KV18 follow. [2, 3, 4, 5, 6, 7]

Operation	K	LD	R/W	DQ	DQ
Write cycle: Load address; wait one cycle; input write data on consecutive K and \overline{K} rising edges.	L–H	L	L	D(A1) at K(t + 1) ↑	D(A2) at $\overline{K}(t + 1) \uparrow$
Read cycle: Load address; wait one and a half cycle; read data on consecutive \overline{C} and C rising edges.	L–H	L	Н	Q(A1) at $\overline{C}(t + 1)^{\uparrow}$	Q(A2) at C(t + 2) 1
NOP: No operation	L–H	Н	Х	High Z	High Z
Standby: Clock stopped	Stopped	Х	Х	Previous State	Previous State

Burst Address Table

(CY7C1318KV18, CY7C1320KV18)

First Address (External)	Second Address (Internal)				
XX0	XX1				
XX1	XX0				

Notes

- 2. X = 'Don't Care', H = Logic HIGH, L = Logic LOW, ↑ represents rising edge.
- Device powers up deselected with the outputs in a tristate condition.
 On CY7C1318KV18 and CY7C1320KV18, 'A1' represents address location latched by the devices when transaction was initiated and 'A2' represents the addresses
- 5. 't' represents the cycle at which a read/write operation is started. t + 1 and t + 2 are the first and second clock cycles succeeding the 't' clock cycle.
- 6. Data inputs are registered at K and K rising edges. Data outputs are delivered on C and C rising edges, except when in single clock mode.
- Ensure that when the clock is stopped K = K and C = C = HIGH. This is not essential, but permits most rapid restart by overcoming transmission line charging symmetrically.



Write Cycle Descriptions

The write cycle description table for CY7C1318KV18 follows. $^{[8,\ 9]}$

BWS ₀	BWS ₁	K	ĸ	Comments
L	L	L–H	ı	During the data portion of a write sequence: CY7C1318KV18 – both bytes (D _[17:0]) are written into the device.
L	L	I	I.	During the data portion of a write sequence: CY7C1318KV18 – both bytes (D _[17:0]) are written into the device.
L	Н	L–H	1	During the data portion of a write sequence: CY7C1318KV18 – only the lower byte $(D_{[8:0]})$ is written into the device, $D_{[17:9]}$ remains unaltered.
L	Н	-	L–H	During the data portion of a write sequence: CY7C1318KV18 – only the lower byte $(D_{[8:0]})$ is written into the device, $D_{[17:9]}$ remains unaltered.
Н	L	L–H	-	During the data portion of a write sequence: CY7C1318KV18 – only the upper byte $(D_{[17:9]})$ is written into the device, $D_{[8:0]}$ remains unaltered.
Н	L	-	L–H	During the data portion of a write sequence: CY7C1318KV18 – only the upper byte $(D_{[17:9]})$ is written into the device, $D_{[8:0]}$ remains unaltered.
Н	Н	L–H	-	No data is written into the devices during this portion of a write operation.
Н	Н	_	L–H	No data is written into the devices during this portion of a write operation.

Document Number: 001-58905 Rev. *L

Notes
8. X = 'Don't Care', H = Logic HIGH, L = Logic LOW, ↑ represents rising edge.
9. Is based on a write cycle that was initiated in accordance with the Truth Table on page 9. BWS₀, BWS₁, BWS₂, and BWS₃ can be altered on different portions of a write cycle, as long as the setup and hold requirements are achieved.



Write Cycle Descriptions

The write cycle description table for CY7C1320KV18 follows. [10, 11]

BWS ₀	BWS ₁	BWS ₂	BWS ₃	K	K	Comments
L	L	L	L	L–H	ı	During the data portion of a write sequence, all four bytes ($D_{[35:0]}$) are written into the device.
L	L	L	L	-	L–H	During the data portion of a write sequence, all four bytes ($D_{[35:0]}$) are written into the device.
L	Н	Η	Η	L–H	1	During the data portion of a write sequence, only the lower byte $(D_{[8:0]})$ is written into the device. $D_{[35:9]}$ remains unaltered.
L	Н	Η	Η	-	L–H	During the data portion of a write sequence, only the lower byte ($D_{[8:0]}$) is written into the device. $D_{[35:9]}$ remains unaltered.
Н	L	Η	Ι	L–H	1	During the data portion of a write sequence, only the byte $(D_{[17:9]})$ is written into the device. $D_{[8:0]}$ and $D_{[35:18]}$ remains unaltered.
Н	L	Ι	Η	-	L–H	During the data portion of a write sequence, only the byte $(D_{[17:9]})$ is written into the device. $D_{[8:0]}$ and $D_{[35:18]}$ remains unaltered.
Н	Н	L	Η	L–H	ı	During the data portion of a write sequence, only the byte $(D_{[26:18]})$ is written into the device. $D_{[17:0]}$ and $D_{[35:27]}$ remains unaltered.
Н	Н	L	Н	-	L–H	During the data portion of a write sequence, only the byte $(D_{[26:18]})$ is written into the device. $D_{[17:0]}$ and $D_{[35:27]}$ remains unaltered.
Н	Н	I	L	L–H	ı	During the data portion of a write sequence, only the byte $(D_{[35:27]})$ is written into the device. $D_{[26:0]}$ remains unaltered.
Н	Н	Η	L	_	L–H	During the data portion of a write sequence, only the byte $(D_{[35:27]})$ is written into the device. $D_{[26:0]}$ remains unaltered.
Н	Н	Н	Н	L–H	_	No data is written into the device during this portion of a write operation.
Н	Н	Н	Н	_	L–H	No data is written into the device during this portion of a write operation.

Document Number: 001-58905 Rev. *L

Notes
 10. X = 'Don't Care', H = Logic HIGH, L = Logic LOW, ↑ represents rising edge.
 11. Is based on a write cycle that was initiated in accordance with the Truth Table on page 9. BWS₀, BWS₁, BWS₂, and BWS₃ can be altered on different portions of a write cycle, as long as the setup and hold requirements are achieved.



IEEE 1149.1 Serial Boundary Scan (JTAG)

These SRAMs incorporate a serial boundary scan test access port (TAP) in the FBGA package. This part is fully compliant with IEEE Standard #1149.1-2001. The TAP operates using JEDEC standard 1.8 V I/O logic levels.

Disabling the JTAG Feature

It is possible to operate the SRAM without using the JTAG feature. To disable the TAP controller, TCK must be tied LOW (V_{SS}) to prevent clocking of the device. TDI and TMS are internally pulled up and may be unconnected. They may alternatively be connected to V_{DD} through a pull up resistor. TDO must be left unconnected. Upon power up, the device comes up in a reset state, which does not interfere with the operation of the device.

Test Access Port

Test Clock

The test clock is used only with the TAP controller. All inputs are captured on the rising edge of TCK. All outputs are driven from the falling edge of TCK.

Test Mode Select (TMS)

The TMS input is used to give commands to the TAP controller and is sampled on the rising edge of TCK. This pin may be left unconnected if the TAP is not used. The pin is pulled up internally, resulting in a logic HIGH level.

Test Data-In (TDI)

The TDI pin is used to serially input information into the registers and can be connected to the input of any of the registers. The register between TDI and TDO is chosen by the instruction that is loaded into the TAP instruction register. For information about loading the instruction register, see the TAP Controller State Diagram on page 14. TDI is internally pulled up and can be unconnected if the TAP is unused in an application. TDI is connected to the most significant bit (MSB) on any register.

Test Data-Out (TDO)

The TDO output pin is used to serially clock data out from the registers. The output is active, depending upon the current state of the TAP state machine (see Instruction Codes on page 18). The output changes on the falling edge of TCK. TDO is connected to the least significant bit (LSB) of any register.

Performing a TAP Reset

A Reset is performed by forcing TMS HIGH (V_{DD}) for five rising edges of TCK. This Reset does not affect the operation of the SRAM and is performed when the SRAM is operating. At power up, the TAP is reset internally to ensure that TDO comes up in a High Z state.

TAP Registers

Registers are connected between the TDI and TDO pins to scan the data in and out of the SRAM test circuitry. Only one register can be selected at a time through the instruction registers. Data is serially loaded into the TDI pin on the rising edge of TCK. Data is output on the TDO pin on the falling edge of TCK.

Instruction Register

Three-bit instructions are serially loaded into the instruction register. This register is loaded when it is placed between the TDI and TDO pins, as shown in TAP Controller Block Diagram on page 15. Upon power up, the instruction register is loaded with the IDCODE instruction. It is also loaded with the IDCODE instruction if the controller is placed in a reset state, as described in the previous section.

When the TAP controller is in the Capture-IR state, the two least significant bits are loaded with a binary "01" pattern to allow for fault isolation of the board level serial test path.

Bypass Register

To save time when serially shifting data through registers, it is sometimes advantageous to skip certain chips. The bypass register is a single-bit register that can be placed between TDI and TDO pins. This enables shifting of data through the SRAM with minimal delay. The bypass register is set LOW (V_{SS}) when the BYPASS instruction is executed.

Boundary Scan Register

The boundary scan register is connected to all the input and output pins on the SRAM. Several No Connect (NC) pins are also included in the scan register to reserve pins for higher density devices

The boundary scan register is loaded with the contents of the RAM input and output ring when the TAP controller is in the Capture-DR state and is then placed between the TDI and TDO pins when the controller is moved to the Shift-DR state. The EXTEST, SAMPLE/PRELOAD, and SAMPLE Z instructions are used to capture the contents of the input and output ring.

The Boundary Scan Order on page 19 shows the order in which the bits are connected. Each bit corresponds to one of the bumps on the SRAM package. The MSB of the register is connected to TDI, and the LSB is connected to TDO.

Identification (ID) Register

The ID register is loaded with a vendor-specific, 32-bit code during the Capture-DR state when the IDCODE command is loaded in the instruction register. The IDCODE is hardwired into the SRAM and is shifted out when the TAP controller is in the Shift-DR state. The ID register has a vendor code and other information described in Identification Register Definitions on page 18.

TAP Instruction Set

Eight different instructions are possible with the three-bit instruction register. All combinations are listed in Instruction Codes on page 18. Three of these instructions are listed as RESERVED and must not be used. The other five instructions are described in this section in detail.

Instructions are loaded into the TAP controller during the Shift-IR state when the instruction register is placed between TDI and TDO. During this state, instructions are shifted through the instruction register through the TDI and TDO pins. To execute the instruction after it is shifted in, the TAP controller must be moved into the Update-IR state.



IDCODE

The IDCODE instruction loads a vendor-specific, 32-bit code into the instruction register. It also places the instruction register between the TDI and TDO pins and shifts the IDCODE out of the device when the TAP controller enters the Shift-DR state. The IDCODE instruction is loaded into the instruction register at power up or whenever the TAP controller is supplied a Test-Logic-Reset state.

SAMPLE Z

The SAMPLE Z instruction connects the boundary scan register between the TDI and TDO pins when the TAP controller is in a Shift-DR state. The SAMPLE Z command puts the output bus into a High Z state until the next command is supplied during the Update IR state.

SAMPLE/PRELOAD

SAMPLE/PRELOAD is a 1149.1 mandatory instruction. When the SAMPLE/PRELOAD instructions are loaded into the instruction register and the TAP controller is in the Capture-DR state, a snapshot of data on the input and output pins is captured in the boundary scan register.

The TAP controller clock can only operate at a frequency up to 20 MHz, while the SRAM clock operates more than an order of magnitude faster. Because there is a large difference in the clock frequencies, it is possible that during the Capture-DR state, an input or output undergoes a transition. The TAP may then try to capture a signal while in transition (metastable state). This does not harm the device, but there is no guarantee as to the value that is captured. Repeatable results may not be possible.

To guarantee that the boundary scan register captures the correct value of a signal, the SRAM signal must be stabilized long enough to meet the TAP controller's capture setup plus hold times (t_{CS} and t_{CH}). The SRAM clock input might not be captured correctly if there is no way in a design to stop (or slow) the clock during a SAMPLE/PRELOAD instruction. If this is an issue, it is still possible to capture all other signals and simply ignore the value of the CK and $\overline{\text{CK}}$ captured in the boundary scan register.

After the data is captured, it is possible to shift out the data by putting the TAP into the Shift-DR state. This places the boundary scan register between the TDI and TDO pins.

PRELOAD places an initial data pattern at the latched parallel outputs of the boundary scan register cells before the selection of another boundary scan test operation.

The shifting of data for the SAMPLE and PRELOAD phases can occur concurrently when required, that is, while the data captured is shifted out, the preloaded data can be shifted in.

BYPASS

When the BYPASS instruction is loaded in the instruction register and the TAP is placed in a Shift-DR state, the bypass register is placed between the TDI and TDO pins. The advantage of the BYPASS instruction is that it shortens the boundary scan path when multiple devices are connected together on a board.

EXTEST

The EXTEST instruction drives the preloaded data out through the system output pins. This instruction also connects the boundary scan register for serial access between the TDI and TDO in the Shift-DR controller state.

EXTEST OUTPUT BUS TRISTATE

IEEE Standard 1149.1 mandates that the TAP controller be able to put the output bus into a tristate mode.

The boundary scan register has a special bit located at bit #47. When this scan cell, called the 'extest output bus tristate', is latched into the preload register during the Update-DR state in the TAP controller, it directly controls the state of the output (Q-bus) pins, when the EXTEST is entered as the current instruction. When HIGH, it enables the output buffers to drive the output bus. When LOW, this bit places the output bus into a High Z condition.

This bit is set by entering the SAMPLE/PRELOAD or EXTEST command, and then shifting the desired bit into that cell, during the Shift-DR state. During Update-DR, the value loaded into that shift-register cell latches into the preload register. When the EXTEST instruction is entered, this bit directly controls the output Q-bus pins. Note that this bit is preset HIGH to enable the output when the device is powered up, and also when the TAP controller is in the Test-Logic-Reset state.


Reserved

These instructions are not implemented but are reserved for future use. Do not use these instructions.



TAP Controller State Diagram

The state diagram for the TAP controller follows. [12]




Note

^{12.} The 0/1 next to each state represents the value at TMS at the rising edge of TCK.



TAP Controller Block Diagram



TAP Electrical Characteristics

Over the Operating Range

Parameter [13, 14, 15]	Description	Test Conditions	Min	Max	Unit
V _{OH1}	Output HIGH voltage	$I_{OH} = -2.0 \text{ mA}$	1.4	-	V
V _{OH2}	Output HIGH voltage	$I_{OH} = -100 \mu A$	1.6	-	V
V _{OL1}	Output LOW voltage	I _{OL} = 2.0 mA	-	0.4	V
V_{OL2}	Output LOW voltage	I _{OL} = 100 μA	-	0.2	V
V_{IH}	Input HIGH voltage	_	$0.65 \times V_{DD}$	V _{DD} + 0.3	V
V_{IL}	Input LOW voltage	_	-0.3	$0.35 \times V_{DD}$	V
I _X	Input and output load current	$GND \leq V_I \leq V_DD$	– 5	5	μА

Notes

^{13.} These characteristics pertain to the TAP inputs (TMS, TCK, TDI and TDO). Parallel load levels are specified in the Electrical Characteristics on page 21.

14. Overshoot: V_{IH(AC)} < V_{DDQ} + 0.85 V (Pulse width less than t_{CYC}/2), Undershoot: V_{IL(AC)} > -1.5 V (Pulse width less than t_{CYC}/2).

15. All voltage referenced to Ground.



TAP AC Switching Characteristics

Over the Operating Range

7] Description	Min	Max	Unit
TCK Clock Cycle Time	50	_	ns
TCK Clock Frequency	_	20	MHz
TCK Clock HIGH	20	_	ns
TCK Clock LOW	20	_	ns
	-	•	
TMS Setup to TCK Clock Rise	5	_	ns
TDI Setup to TCK Clock Rise	5	_	ns
Capture Setup to TCK Rise	5	_	ns
	-	•	
TMS Hold after TCK Clock Rise	5	_	ns
TDI Hold after Clock Rise	5	_	ns
Capture Hold after clock rise	5	_	ns
	-	•	
TCK Clock LOW to TDO Valid	_	10	ns
TCK Clock LOW to TDO Invalid	0	_	ns
	TCK Clock Cycle Time TCK Clock Frequency TCK Clock HIGH TCK Clock LOW TMS Setup to TCK Clock Rise TDI Setup to TCK Clock Rise Capture Setup to TCK Rise TMS Hold after TCK Clock Rise TDI Hold after Clock Rise Capture Hold after clock rise TCK Clock LOW to TDO Valid	TCK Clock Cycle Time 50 TCK Clock Frequency - TCK Clock HIGH 20 TCK Clock LOW 20 TMS Setup to TCK Clock Rise 5 TDI Setup to TCK Clock Rise 5 Capture Setup to TCK Rise 5 TMS Hold after TCK Clock Rise 5 TDI Hold after Clock Rise 5 TDI Hold after Clock Rise 5 TCK Clock LOW 5 TMS Hold after TCK Clock Rise 5 TDI Hold after Clock Rise 5 TCK Clock LOW to TDO Valid -	TCK Clock Cycle Time 50 - TCK Clock Frequency - 20 TCK Clock HIGH 20 - TCK Clock LOW 20 - TMS Setup to TCK Clock Rise 5 - TDI Setup to TCK Clock Rise 5 - Capture Setup to TCK Rise 5 - TMS Hold after TCK Clock Rise 5 - TDI Hold after Clock Rise 5 - Capture Hold after clock rise 5 - TCK Clock LOW to TDO Valid - 10


^{16.} t_{CS} and t_{CH} refer to the setup and hold time requirements of latching data from the boundary scan register. 17. Test conditions are specified using the load in TAP AC Test Conditions. t_R/t_F = 1 ns.



TAP Timing and Test Conditions

Figure 3 shows the TAP timing and test conditions. [18]

Figure 3. TAP Timing and Test Conditions



^{18.} Test conditions are specified using the load in TAP AC Test Conditions. t_R/t_F = 1 ns.



Identification Register Definitions

Instruction Field	Value		Description	
instruction rieta	CY7C1318KV18	CY7C1320KV18	Description	
Revision number (31:29)	000	000	Version number.	
Cypress device ID (28:12)	11010100010010101	11010100010100101	Defines the type of SRAM.	
Cypress JEDEC ID (11:1)	00000110100	00000110100	Allows unique identification of SRAM vendor.	
ID register presence (0)	1	1	Indicates the presence of an ID register.	

Scan Register Sizes

Register Name	Bit Size
Instruction	3
Bypass	1
ID	32
Boundary Scan	107

Instruction Codes

Instruction	Code	Description
EXTEST	000	Captures the input and output ring contents.
IDCODE	001	Loads the ID register with the vendor ID code and places the register between TDI and TDO. This operation does not affect SRAM operation.
SAMPLE Z	010	Captures the input and output contents. Places the boundary scan register between TDI and TDO. Forces all SRAM output drivers to a High Z state.
RESERVED	011	Do not use: This instruction is reserved for future use.
SAMPLE/PRELOAD	100	Captures the input and output ring contents. Places the boundary scan register between TDI and TDO. Does not affect the SRAM operation.
RESERVED	101	Do not use: This instruction is reserved for future use.
RESERVED	110	Do not use: This instruction is reserved for future use.
BYPASS	111	Places the bypass register between TDI and TDO. This operation does not affect SRAM operation.

Document Number: 001-58905 Rev. *L



Boundary Scan Order

Bit #	Bump ID
0	6R
1	6P
2	6N
3	7P
4	7N
5	7R
6	8R
7	8P
8	9R
9	11P
10	10P
11	10N
12	9P
13	10M
14	11N
15	9M
16	9N
17	11L
18	11M
19	9L
20	10L
21	11K
22	10K
23	9J
24	9K
25	10J
26	11J
27	11H

Bit #	Bump ID
28	10G
29	9G
30	11F
31	11G
32	9F
33	10F
34	11E
35	10E
36	10D
37	9E
38	10C
39	11D
40	9C
41	9D
42	11B
43	11C
44	9B
45	10B
46	11A
47	Internal
48	9A
49	8B
50	7C
51	6C
52	8A
53	7A
54	7B
55	6B

Bit#	Bump ID		
56	6A		
57	5B		
58	5A		
59	4A		
60	5C		
61	4B		
62	3A		
63	1H		
64	1A		
65	2B		
66	3B		
67	1C		
68	1B		
69	3D		
70	3C		
71	1D		
72	2C		
73	3E		
74	2D		
75	2E		
76	1E		
77	2F		
78	3F		
79	1G		
80	1F		
81	3G		
82	2G		
83	1J		

Bit #	Bump ID
84	2J
85	3K
86	3J
87	2K
88	1K
89	2L
90	3L
91	1M
92	1L
93	3N
94	3M
95	1N
96	2M
97	3P
98	2N
99	2P
100	1P
101	3R
102	4R
103	4P
104	5P
105	5N
106	5R



Power Up Sequence in DDR II SRAM

DDR II SRAMs must be powered up and initialized in a predefined manner to prevent undefined operations.


Power Up Sequence

- Apply power and drive DOFF either HIGH or LOW (All other inputs can be HIGH or LOW).
- □ Apply V_{DD} before V_{DDQ} .
 □ Apply $\underline{V_{DDQ}}$ before V_{REF} or at the same time as V_{REF} .
 □ Drive DOFF HIGH.
- Provide stable DOFF (HIGH), power and clock (K, K) for 20 µs to lock the PLL.

PLL Constraints

- PLL uses K clock as its synchronizing input. The input must have low phase jitter, which is specified as $t_{\mbox{\scriptsize KC Var}}$
- The PLL functions at frequencies down to 120 MHz.
- If the input clock is unstable and the PLL is enabled, then the PLL may lock onto an incorrect frequency, causing unstable SRAM behavior. To avoid this, provide 20 µs of stable clock to relock to the desired clock frequency.

Figure 4. Power Up Waveforms





Maximum Ratings

Exceeding maximum ratings may impair the useful life of the device. These user guidelines are not tested.

device. These deel galdelines are not tested.
Storage temperature—65 °C to +150 °C
Ambient temperature with power applied–55 °C to +125 °C
Supply voltage on $\rm V_{DD}$ relative to GND–0.5 V to +2.9 V
Supply voltage on $\rm V_{DDQ}$ relative to GND –0.5 V to +V $_{DD}$
DC applied to outputs in High Z–0.5 V to $\rm V_{DDQ}$ + 0.3 V
DC input voltage ^[19] 0.5 V to V _{DD} + 0.3 V
Current into outputs (LOW)20 mA
Static discharge voltage
(MIL-STD-883, M 3015)> 2001 V
Latch up current > 200 mA

Operating Range

Range	Range Ambient Temperature (T _A)		V _{DDQ} ^[20]
Commercial	0 °C to +70 °C	1.8 ± 0.1 V	1.4 V to
Industrial	–40 °C to +85 °C		V_{DD}

Neutron Soft Error Immunity

Parameter	Description	Test Conditions	Тур	Max*	Unit
LSBU	Logical single-bit upsets	25 °C	197	216	FIT/ Mb
LMBU	Logical multi-bit upsets	25 °C	0	0.01	FIT/ Mb
SEL	Single event latch up	85 °C	0	0.1	FIT/ Dev

^{*} No LMBU or SEL events occurred during testing; this column represents a statistical χ^2 , 95% confidence limit calculation. For more details refer to Application Note, Accelerated Neutron SER Testing and Calculation of Terrestrial Failure Rates - AN 54908.

Electrical Characteristics

Over the Operating Range

DC Electrical Characteristics

Over the Operating Range

Parameter [21]	Description	Test Conditions	Min	Тур	Max	Unit
V_{DD}	Power supply voltage	_	1.7	1.8	1.9	V
V_{DDQ}	IO supply voltage	_	1.4	1.5	V_{DD}	V
V _{OH}	Output HIGH voltage	Note 22	V _{DDQ} /2 – 0.12	-	$V_{DDQ}/2 + 0.12$	V
V _{OL}	Output LOW voltage	Note 23	V _{DDQ} /2 – 0.12	-	V _{DDQ} /2 + 0.12	V
V _{OH(LOW)}	Output HIGH voltage	I _{OH} = -0.1 mA, nominal impedance	V _{DDQ} – 0.2	_	V_{DDQ}	V
$V_{OL(LOW)}$	Output LOW voltage	I _{OL} = 0.1 mA, nominal impedance	V _{SS}	_	0.2	V
V _{IH}	Input HIGH voltage	_	V _{REF} + 0.1	_	V _{DDQ} + 0.3	V
V_{IL}	Input LOW voltage	_	-0.3	-	V _{REF} – 0.1	V
I _X	Input leakage current	$GND \le V_I \le V_{DDQ}$	-5	-	5	μΑ
I _{OZ}	Output leakage current	$GND \le V_I \le V_{DDQ}$, output disabled	-5	-	5	μΑ
V _{REF}	Input reference voltage [24]	Typical value = 0.75 V	0.68	0.75	0.95	V

^{19.} Overshoot: $V_{IH(AC)} < V_{DDQ} + 0.85 \text{ V}$ (Pulse width less than $t_{CYC}/2$), Undershoot: $V_{IL(AC)} > -1.5 \text{ V}$ (Pulse width less than $t_{CYC}/2$). 20. Power up: assumes a linear ramp from 0 V to $V_{DD(min)}$ within 200 ms. During this time $V_{IH} < V_{DD}$ and $V_{DDQ} \le V_{DD}$.

^{21.} All voltage referenced to Ground.

Noting telephone to Ground.
 1. All Voltage reference to Ground.
 22. Outputs are impedance controlled. I_{OL} = (V_{DDQ}/2)/(RQ/5) for values of 175 Ω ≤ RQ ≤ 350 Ω.
 23. Outputs are impedance controlled. I_{OL} = (V_{DDQ}/2)/(RQ/5) for values of 175 Ω ≤ RQ ≤ 350 Ω.
 24. V_{REF(min)} = 0.68 V or 0.46 V_{DDQ}, whichever is larger, V_{REF(max)} = 0.95 V or 0.54 V_{DDQ}, whichever is smaller.



Electrical Characteristics (continued)

Over the Operating Range

DC Electrical Characteristics (continued)

Over the Operating Range

Parameter [21]	Description	Test Condit	tions		Min	Тур	Max	Unit
I _{DD} ^[25]	V _{DD} operating supply	$V_{DD} = Max, I_{OUT} = 0 mA,$	333 MHz	(× 18)	_	_	450	mA
		$f = f_{MAX} = 1/t_{CYC}$		(× 36)	_	_	560	
			300 MHz	(× 18)	_	_	430	mA
				(× 36)	_	_	520	
			250 MHz	(× 18)	_	_	380	mA
				(× 36)	_	_	460	
I _{SB1}	Automatic power down	Max V _{DD} , both ports	333 MHz	(× 18)	_	_	270	mA
	current	deselected, $V_{IN} \ge V_{IH}$ or $V_{IN} \le V_{II}$,		(× 36)	_	_	270	
		$f = f_{MAX} = 1/t_{CYC}$	300 MHz	(× 18)	_	_	260	mA
		inputs static		(× 36)	_	_	260	
			250 MHz	(× 18)	_	_	250	mA
				(× 36)	_	_	250	

Note25. The operation current is calculated with 50% read cycle and 50% write cycle.



AC Electrical Characteristics

Over the Operating Range

Parameter [26]	Description	Test Conditions	Min	Тур	Max	Unit
V _{IH}	Input HIGH voltage	_	V _{REF} + 0.2	-	-	V
V_{IL}	Input LOW voltage	_	-	-	V _{REF} – 0.2	V

Capacitance


Parameter [27]	Description	Test Conditions	Max	Unit
C _{IN}	Input capacitance	$T_A = 25 ^{\circ}\text{C}, f = 1 \text{MHz}, V_{DD} = 1.8 \text{V}, V_{DDQ} = 1.5 \text{V}$	4	pF
C _O	Output capacitance		4	pF

Thermal Resistance

Parameter [27]	Description	Test Conditions	165-ballFBGA Package	Unit
Θ _{JA} (0 m/s)	Thermal resistance Socketed on a 170 × 220 × 2.35 mm, eight-layer printed	18.96	°C/W	
Θ _{JA} (1 m/s)	(junction to ambient)	circuit board	17.89	°C/W
Θ _{JA} (3 m/s)			17.12	°C/W
Θ_{JB}	Thermal resistance (junction to board)		15.94	°C/W
$\Theta_{\sf JC}$	Thermal resistance (junction to case)		5.79	°C/W

AC Test Loads and Waveforms

Figure 5. AC Test Loads and Waveforms



- 26. Overshoot: V_{IH(AC)} < V_{DDQ} + 0.85 V (Pulse width less than t_{CYC}/2), Undershoot: V_{IL(AC)} > -1.5 V (Pulse width less than t_{CYC}/2).

 27. Tested initially and after any design or process change that may affect these parameters.

 28. Unless otherwise noted, test conditions assume signal transition time of 2 V/ns, timing reference levels of 0.75 V, V_{REF} = 0.75 V, RQ = 250 Ω, V_{DDQ} = 1.5 V, input pulse levels of 0.25 V to 1.25 V, and output loading of the specified I_{OL}/I_{OH} and load capacitance shown in (a) of Figure 5.



Switching Characteristics

Over the Operating Range

Parameter [29, 30]			333 MHz		300	MHz	250 MHz		
Cypress Parameter	Consortium Parameter	Description	Min	Max	Min	Max	Min	Max	Unit
t _{POWER}	_	V _{DD(typical)} to the First Access ^[31]	1	_	1	-	1	_	ms
t _{CYC}	t _{KHKH}	K Clock and C Clock Cycle Time	3.0	8.4	3.3	8.4	4.0	8.4	ns
t _{KH}	t _{KHKL}	Input Clock (K/K and C/C) HIGH	1.20	_	1.32	_	1.6	-	ns
t _{KL}	t _{KLKH}	Input Clock (K/K and C/C) LOW	1.20	_	1.32	-	1.6	_	ns
t _{KHK} H	^t ĸн к н	K Clock Rise to K Clock Rise and C to C Rise (rising edge to rising edge)	1.35	-	1.49	-	1.8	_	ns
t _{KHCH}	t _{KHCH}	K/K Clock Rise to C/C Clock Rise (rising edge to rising edge)	0.0	1.30	0.0	1.45	0.0	1.8	ns
Setup Time	s			•	•	•	•	•	•
t _{SA}	t _{AVKH}	Address Setup to K Clock Rise	0.4	_	0.4	_	0.5	_	ns
t _{SC}	t _{IVKH}	Control Setup to K Clock Rise (LD, R/W)	0.4	-	0.4	_	0.5	_	ns
t _{SCDDR}	t _{IVKH}	Double Data Rate Control Setup to Clock (K/K) Rise (BWS ₀ , BWS ₁ , BWS ₂ , BWS ₃)	0.3	-	0.3	_	0.35	_	ns
t _{SD}	t _{DVKH}	$D_{[X:0]}$ Setup to Clock (K/ \overline{K}) Rise	0.3	_	0.3	_	0.35	_	ns
Hold Times									
t _{HA}	t _{KHAX}	Address Hold after K Clock Rise	0.4	_	0.4	_	0.5	_	ns
t _{HC}	t _{KHIX}	Control Hold after K Clock Rise (LD, R/W)	0.4	_	0.4	_	0.5	_	ns
t _{HCDDR}	t _{KHIX}	Double Data Rate Control Hold after Clock (K/K) Rise (BWS ₀ , BWS ₁ , BWS ₂ , BWS ₃)	0.3	_	0.3	_	0.35	_	ns
t _{HD}	t _{KHDX}	D _[X:0] Hold after Clock (K/K) Rise	0.3	_	0.3	_	0.35	_	ns

Document Number: 001-58905 Rev. *L

 ^{29.} Unless otherwise noted, test conditions assume signal transition time of 2 V/ns, timing reference levels of 0.75 V, V_{REF} = 0.75 V, RQ = 250 Ω, V_{DDQ} = 1.5 V, input pulse levels of 0.25 V to 1.25 V, and output loading of the specified l_{OL}/l_{OH} and load capacitance shown in (a) of Figure 5 on page 23.
 30. When a part with a maximum frequency above 167 MHz is operating at a lower clock frequency, it requires the input timings of the frequency range in which it is operated and outputs data with the output timings of that frequency range.
 31. This part has an internal voltage regulator; t_{POWER} is the time that the power is supplied above V_{DD(min)} initially before a read or write operation can be initiated.



Switching Characteristics (continued)

Over the Operating Range

Parame	ter ^[29, 30]		333 MHz		300	300 MHz		250 MHz	
Cypress Parameter	Consortium Parameter	Description	Min	Max	Min	Max	Min	Max	Unit
Output Tim	ies								
t _{CO}	t _{CHQV}	C/C Clock Rise (or K/K in single clock mode) to Data Valid	_	0.45	_	0.45	_	0.45	ns
t _{DOH}	t _{CHQX}	Data Output Hold after Output C/C Clock Rise (Active to Active)	-0.45	-	-0.45	-	-0.45	_	ns
t _{CCQO}	t _{CHCQV}	C/C Clock Rise to Echo Clock Valid	_	0.45	_	0.45	-	0.45	ns
t _{CQOH}	t _{CHCQX}	Echo Clock Hold after C/C Clock Rise	-0.45	-	-0.45	_	-0.45	_	ns
t _{CQD}	t _{CQHQV}	Echo Clock High to Data Valid	_	0.25	_	0.27	_	0.30	ns
t _{CQDOH}	t _{CQHQX}	Echo Clock High to Data Invalid	-0.25	_	-0.27	_	-0.30	_	ns
t _{CQH}	t _{CQHCQL}	Output Clock (CQ/CQ) HIGH[32]	1.25	_	1.40	_	1.75	_	ns
t _{CQH} CQH	t _{CQH} CQH	CQ Clock Rise to \overline{CQ} Clock Rise (rising edge to rising edge) [32]	1.25	-	1.40	-	1.75	_	ns
t _{CHZ}	t _{CHQZ}	Clock (C/ \overline{C}) Rise to High Z (Active to High Z) [33, 34]	-	0.45	_	0.45	-	0.45	ns
t _{CLZ}	t _{CHQX1}	Clock (C/C) Rise to Low Z [33, 34]	-0.45	_	-0.45	-	-0.45	_	ns
PLL Timing)								•
t _{KC Var}	t _{KC Var}	Clock Phase Jitter	_	0.20	_	0.20	_	0.20	ns
t _{KC lock}	t _{KC lock}	PLL Lock Time (K, C) [35]	20	_	20	-	20	_	μS
t _{KC Reset}	t _{KC Reset}	K Static to PLL Reset	30	_	30	_	30	_	ns

Document Number: 001-58905 Rev. *L


 ^{32.} These parameters are extrapolated from the input timing parameters (t_{CYC}/2 – 250 ps, where 250 ps is the internal jitter). These parameters are only guaranteed by design and are not tested in production.
 33. t_{CHZ}, t_{CLZ} are specified with a load capacitance of 5 pF as in (b) of Figure 5 on page 23. Transition is measured ±100 mV from steady-state voltage.
 34. At any voltage and temperature t_{CHZ} is less than t_{CLZ} and t_{CHZ} less than t_{CO}.
 35. For frequencies 300 MHz or below, the Cypress QDR II devices surpass the QDR consortium specification for PLL lock time (t_{KC} lock) of 20 μs (min. spec.) and will lock after 1024 clock cycles (min. spec.), after a stable clock is presented, per the previous 90 nm version.



Switching Waveforms

Read/Write/Deselect Sequence

Figure 6. Read/Write/Deselect Sequence [36, 37, 38]



^{36.} Q00 refers to output from address A0. Q01 refers to output from the next internal burst address following A0, that is, A0 + 1.

^{37.} Outputs are disabled (High Z) one clock cycle after a NOP.
38. In this example, if address A4 = A3, then data Q40 = D30 and Q41 = D31. Write data is forwarded immediately as read results. This note applies to the whole diagram.




Ordering Information

The following table contains only the parts that are currently available. If you do not see what you are looking for, contact your local sales representative. For more information, visit the Cypress website at www.cypress.com/products and refer to the product summary page at http://www.cypress.com/products

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives and distributors. To find the office closest to you, visit us at http://www.cypress.com/go/datasheet/offices.

Speed (MHz)	Ordering Code	Package Diagram	Package Type	Operating Range
250	CY7C1318KV18-250BZC	51-85180	165-ball FBGA (13 × 15 × 1.4 mm)	Commercial
	CY7C1320KV18-250BZC			
	CY7C1318KV18-250BZXC		165-ball FBGA (13 × 15 × 1.4 mm) Pb-free	
	CY7C1320KV18-250BZXC			
	CY7C1318KV18-250BZI		165-ball FBGA (13 × 15 × 1.4 mm)	Industrial
	CY7C1320KV18-250BZI			
	CY7C1318KV18-250BZXI		165-ball FBGA (13 × 15 × 1.4 mm) Pb-free	
	CY7C1320KV18-250BZXI			
300	CY7C1318KV18-300BZXC	51-85180	165-ball FBGA (13 × 15 × 1.4 mm) Pb-free	Commercial
333	CY7C1320KV18-333BZXC	51-85180	165-ball FBGA (13 × 15 × 1.4 mm) Pb-free	Commercial


Ordering Code Definitions






Package Diagram

Figure 7. 165-ball FBGA (13 × 15 × 1.4 mm) BB165D/BW165D (0.5 Ball Diameter) Package Outline, 51-85180



NOTES:
SOLDER PAD TYPE: NON-SOLDER MASK DEFINED (NSMD)
JEDEC REFERENCE: MO-216 / ISSUE E
PACKAGE CODE: BBOAC/BWOAC
PACKAGE WEIGHT: SEE CYPRESS PACKAGE MATERIAL DECLARATION
DATASHEET (PMDD) POSTED ON THE CYPRESS WEB.



51-85180 *G



Acronyms

Acronym	Description			
DDR	Double Data Rate			
FBGA	ine-Pitch Ball Grid Array			
HSTL	High-Speed Transceiver Logic			
I/O	Input/Output			
JTAG	Joint Test Action Group			
LMBU	Logical Multiple Bit Upset			
LSB	Least Significant Bit			
LSBU	Logical Single Bit Upset			
MSB	Most Significant Bit			
PLL	Phase Locked Loop			
SEL	Single Event Latch-up			
SRAM	Static Random Access Memory			
TAP	Test Access Port			
TCK	Test Clock			
TMS	Test Mode Select			
TDI	Test Data-In			
TDO	Test Data-Out			

Document Conventions

Units of Measure

Symbol	Unit of Measure
°C	degree Celsius
kΩ	kilohm
MHz	megahertz
μΑ	microampere
μs	microsecond
mA	milliampere
mm	millimeter
ms	millisecond
mV	millivolt
ns	nanosecond
Ω	ohm
pF	picofarad
%	percent
V	volt
W	watt



Document History Page

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	2860800	VKN	01/20/2010	New data sheet.
*A	2897150	NJY	03/22/2010	Updated Ordering Information (Removed Inactive parts).
*B	3076901	NJY	11/03/2010	Changed status from Preliminary to Final. Updated Ordering Information (Updated part numbers) and added Ordering Code Definitions. Added Acronyms and Units of Measure.
*C	3169007	NJY	02/10/2011	Updated Switching Characteristics (Added Note 35 and referred the same no in the description of t _{KC lock} parameter). Updated Ordering Information (Updated part numbers).
*D	3374282	VIDB	09/19/2011	Updated Ordering Information (Updated part numbers). Updated to new template.
*E	3451248	VIDB	12/06/2011	Updated Package Diagram.
*F	3596100 3861547	PRIT	04/23/2012	Updated Features (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Configurations (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Functional Description (Removed CY7C1316KV18, CY7C1916KV17 related information). Updated Selection Guide (Removed 167 MHz and 200 MHz frequencies related information, removed CY7C1316KV18, CY7C1916KV18 related information). Removed Logic Block Diagram – CY7C1316KV18. Removed Logic Block Diagram – CY7C1316KV18. Removed Logic Block Diagram – CY7C1316KV18. Updated Pin Configurations (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Pin Definitions (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Functional Overview (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Truth Table (Removed CY7C1316KV18, CY7C1916KV18 related information). Updated Write Cycle Descriptions (Removed CY7C1316KV18 related information). Updated Identification Register Definitions (Removed CY7C1316KV18, CY7C1916KV18). Updated Electrical Characteristics (Updated DC Electrical Characteristics (Removed 167 MHz and 200 MHz frequencies related information), updated Switching Characteristics (Removed 167 MHz and 200 MHz frequencies related information). Updated Package Diagram:
*H	4374859	PRIT	05/09/2014	spec 51-85180 – Changed revision from *E to *F. Updated Application Example: Updated Figure 2. Updated Thermal Resistance: Updated values of Θ_{JA} parameter. Included Θ_{JB} parameter and its details. Updated to new template.



Document History Page (continued)

Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
*	4578255	PRIT	11/25/2014	Updated Functional Description: Added "For a complete list of related documentation, click here." at the end. Updated Ordering Information: Updated part numbers.
*J	5076357	PRIT	01/21/2016	Updated Ordering Information: Updated part numbers. Updated Package Diagram: spec 51-85180 – Changed revision from *F to *G. Updated to new template. Completing Sunset Review.
*K	5126935	PRIT	02/05/2016	Updated Switching Waveforms: Updated Read/Write/Deselect Sequence: Updated Figure 6.
*L	6001917	AESATMP9	12/21/2017	Updated logo and copyright.



Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

Arm® Cortex® Microcontrollers

Automotive

Clocks & Buffers

Interface

Internet of Things

Memory

Microcontrollers

cypress.com/automotive

cypress.com/clocks

cypress.com/interface

cypress.com/iot

cypress.com/memory

cypress.com/mcu

PSoC cypress.com/psoc
Power Management ICs cypress.com/pmic
Touch Sensing cypress.com/touch
USB Controllers cypress.com/usb
Wireless Connectivity cypress.com/wireless

PSoC® Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6 MCU

Cypress Developer Community

Community | Projects | Video | Blogs | Training | Components

Technical Support

cypress.com/support

© Cypress Semiconductor Corporation, 2010-2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software is binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. No computing device can be absolutely secure. Therefore, despite security measures implemented to Cypress hardware or software products. Cypress does not assume any liability arising out of any security breach, such as unauthorized access to or use of a Cypress product. In addition, the products described in these materials may contain design defects or errors known as errata which may cause the product to deviate from published specifications. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not l

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

Document Number: 001-58905 Rev. *L Revised December 21, 2017 Page 32 of 32