

Broadband MMIC: BGA729N6

Low Noise Amplifier for Portable and Mobile TV Applications and FM Radio Application

About this document

Scope and purpose

This application note describes Infineon's BGA729N6 for portable and mobile applications and FM radio application in the range of 70 – 1000 MHz.

1. The BGA729N6 is a Silicon Germanium broadband Low Noise Amplifier (LNA).
2. It supports the portable and mobile TV applications and the FM radio application.
3. In this application note, the performance of BGA729N6 is presented. The circuit requires no external components for matching. The performance is measured on a FR4 board.
4. Key performance parameters at 2.8V, 715 MHz
 - a) High Gain Mode:
Noise Figure = 1.20 dB
Insertion Gain = 16.1 dB
Input return loss = 9.6 dB
Output return loss = 16.5 dB
Input P_{1dB} = -14.1 dBm
 - b) Bypass Mode:
Noise figure = 4.20 dB
Insertion Loss = 4.2 dB
Input return loss = 15.3 dB
Output return loss = 12.2 dB
Input P_{1dB} = 6.0 dBm

Table of Contents

About this document	1
Table of Contents	2
List of Figures ¹	3
List of Tables	4
1 Introduction of Mobile TV and FM Radio Applications	5
1.1 Mobile TV application overview	5
1.2 Infineon's devices for the Mobile TV application	5
1.3 Requirement of the Mobile TV application on the Low Noise Amplifier	5
1.4 FM Radio application overview	6
1.5 BGA729N6 as Low Noise Amplifier for the FM Radio application	6
2 BGA729N6 Overview	7
2.1 Features	7
2.2 Key Applications of BGA729N6	7
2.3 Description	8
3 Application Circuit and Performance Overview	10
3.1 Summary of Measurement Results	10
3.2 BGA729N6 as 70 MHz – 1000 MHz Low Noise Amplifier for Mobile TV and FM Radio Applications ..	14
3.3 Schematics and Bill-of-Materials	15
4 Measurement Graphs	16
5 Evaluation Board and Layout Information	31
6 Authors	33
7 Reference	33
Revision History	33

List of Figures¹

Figure 1	Application Diagram: Mobile TV and FM Reception in Mobile Phones with Band Selection Switch	5
Figure 2	BGA729N6 in TSNP-6-2	7
Figure 3	Equivalent Circuit of BGA729N6	8
Figure 4	Schematics of the BGA729N6 Application Circuit	15
Figure 5	Insertion Power Gain (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications	16
Figure 6	Insertion Power Gain (High Gain, Wideband) of BGA729N6 for TV_Radio Applications	16
Figure 7	Noise Figure (High Gain) of BGA729N6 for TV_Radio Applications	17
Figure 8	Input Return Loss (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications	17
Figure 9	Input Return Loss (High Gain, Smith Chart) of BGA729N6 for TV_Radio Applications	18
Figure 10	Output Return Loss (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications	18
Figure 11	Output Return Loss (High Gain, Smith Chart) of BGA729N6 for TV_Radio Applications	19
Figure 12	Reverse Isolation (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications	19
Figure 13	Stability K-factor (High Gain) of BGA729N6 for TV_Radio Applications	20
Figure 14	Stability Mu1-factor (High Gain) of BGA729N6 for TV_Radio Applications	20
Figure 15	Stability Mu2-factor (High Gain) of BGA729N6 for TV_Radio Applications	21
Figure 16	Input 1dB Compression Point (High Gain, 1.8 V) of BGA729N6 for TV_Radio Applications	21
Figure 17	Input 1dB Compression Point (High Gain, 2.8 V) of BGA729N6 for TV_Radio Applications	22
Figure 18	Third-order Interception Point (High Gain, 1.8 V) of BGA729N6 for TV_Radio Applications	22
Figure 19	Third-order Interception Point (High Gain, 2.8 V) of BGA729N6 for TV_Radio Applications	23
Figure 20	Insertion Power Gain (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications	23
Figure 21	Insertion Power Gain (Bypass, Wideband) of BGA729N6 for TV_Radio Applications	24
Figure 22	Noise Figure (Bypass) of BGA729N6 for TV_Radio Applications	24
Figure 23	Input Return Loss (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications	25
Figure 24	Input Return Loss (Bypass, Smith Chart) of BGA729N6 for TV_Radio Applications	25
Figure 25	Output Return Loss (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications	26
Figure 26	Output Return Loss (Bypass, Smith Chart) of BGA729N6 for TV_Radio Applications	26
Figure 27	Reverse Isolation (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications	27
Figure 28	Stability K-factor (Bypass) of BGA729N6 for TV_Radio Applications	27
Figure 29	Stability Mu1-factor (Bypass) of BGA729N6 for TV_Radio Applications	28
Figure 30	Stability Mu2-factor (Bypass) of BGA729N6 for TV_Radio Applications	28
Figure 31	Input 1dB Compression Point (Bypass, 1.8 V) of BGA729N6 for TV_Radio Applications	29
Figure 32	Input 1dB Compression Point (Bypass, 2.8 V) of BGA729N6 for TV_Radio Applications	29
Figure 33	Third-order Interception Point (Bypass, 1.8 V) of BGA729N6 for TV_Radio Applications	30
Figure 34	Third-order Interception Point (Bypass, 2.8 V) of BGA729N6 for TV_Radio Applications	30
Figure 35	Photo Picture of Evaluation Board (overview) <PCB Marking M150901 Rev.1.0>	31
Figure 36	Photo Picture of Evaluation Board (detailed view)	31
Figure 37	PCB Layer Information	32

List of Tables

Table 1	Pin Assignment of BGA729N6	8
Table 2	Gain Mode Selection Truth Table	9
Table 3	Electrical Characteristics (at room temperature) for High Gain Mode $V_{PON} = 2.8V$, $V_{BP} = 0V$	10
Table 4	Electrical Characteristics (at room temperature) for Bypass Mode $V_{PON} = 2.8V$, $V_{BP} = 2.8V$	11
Table 5	Electrical Characteristics (at room temperature) for High Gain Mode.....	12
Table 6	Electrical Characteristics (at room temperature) for Bypass Mode $V_{PON} = 1.8V$, $V_{BP} = 1.8V$	13
Table 7	Bill-of-Materials.....	15

1) The graphs are generated with the simulation program AWR Microwave Office®.

1 Introduction of Mobile TV and FM Radio Applications

1.1 Mobile TV application overview

Mobile phones today are all-in-one devices. They have not only wireless functions for voice and data but also entertainment features. Mobile TV is one of the most fascinating features. It brings live news and entertainment programs onto the phone display and enables people not to miss their favorite programs.




Figure 1 Application Diagram: Mobile TV and FM Reception in Mobile Phones with Band Selection Switch

1.2 Infineon's devices for the Mobile TV application

Infineon's mobile TV LNA BGA729N6 is especially designed for the mobile TV reception with 50-Ohm interfaces, while our RF transistors offer cost-effective solutions to improve the signal-to-noise ratio and therefore the quality of the TV reception. Those LNAs together with Infineon's ESD protection diode from the [ESD108-B1-CSP0201](#) and ESD103-B1-[02EL/02ELS](#) series improve systems' ESD performance up to 8 kV contact discharge (IEC61000-4-2) at the antenna input. The parasitic capacitance is only 0.2 pF.

Infineon's SP3T switch series can be used to switch between the mobile TV tuner IC and the FM tuner IC.

1.3 Requirement of the Mobile TV application on the Low Noise Amplifier

Low Noise Figure & High Gain

An external LNA or LNA module boosts the sensitivity of the system by reducing the overall NF. In addition due to the size constraint, the modem antenna and the receiver FE cannot always be placed close to the transceiver Integrated Circuit (IC). The path loss in front of the integrated LNA on the transceiver IC increases the system NF significantly. An external LNA physically close to the antenna can help to eliminate the path

loss and reduce the system NF. The sensitivity can be improved by several dB, which means a significant increase in the connectivity range

High Linearity (1-dB compression point P_{1dB} and 3rd-order intercept point IP_3): An increased number of bands at the receiver input create strong interference, leading to high requirements in linearity characteristics such as high input 1-dB compression point, 2nd intermodulation (IMD2) products and input IP_3 performance.

Stable Gain:

The portable and mobile TV application ranges from 170 MHz to 960 MHz, a stable gain over this broad frequency range is a key requirement to the mobile TV LNA.

1.4 FM Radio application overview

Frequency Modulation (FM) radio has a long history, starting from its development in 1933. Today, FM radio is an integral part of almost all mobile phones. The headset cable can serve as an antenna for FM reception. Its size (~75 cm) is ideal to have good reception. Nevertheless, no FM reception is possible when the headset is not available.

There is a clear market trend to be able to use FM radio without the headset cable, meaning that the antenna has to be integrated inside the phone. However, there are space constraints on the antenna design. Shrinking the size of the antenna introduces a high loss in the system which reduces the receiver's sensitivity.

1.5 BGA729N6 as Low Noise Amplifier for the FM Radio application

The BGA729N6 also covers the FM radio frequencies, and is a potential solution as low noise amplifier for FM radio application. The LNA is prematched as a 50 Ohm solution, it solves the problem of the short FM antenna in mobile phones through better impedance match between the FM antenna and the FM receiver. Therefore, it can keep the system signal-to-noise ratio as good as with a headset.

2 BGA729N6 Overview

2.1 Features

- Insertion power gain: 16.3 dB
- Insertion Loss in bypass mode: 4.2 dB
- Low noise figure: 1.05 dB / 4.3 dB in high gain / bypass mode
- Low current consumption: 6.3 mA
- Power off function
- Operating frequency: 70 -1000 MHz
- Three-state control: OFF-, Bypass- and High gain- Mode
- Supply voltage: 1.5 V to 3.3 V
- Ultra small TSNP-6-2 leadless package (footprint: 0.7 x 1.1 mm²)
- B7HF Silicon Germanium technology
- No external matching inductor required
- RF input and output internally matched to 50Ω
- Only 2 external SMD components necessary
- 2kV HBM ESD protection (including Al-pin)
- Pb-free (RoHS compliant) package




Figure 2 BGA729N6 in TSNP-6-2



2.2 Key Applications of BGA729N6

The BGA729N6 is a broadband low power low noise amplifier (LNA) MMIC for portable and mobile TV applications and FM radio application.

Broadband MMIC: BGA729N6

Low Noise Amplifier for Portable and Mobile TV Applications and FM Radio

BGA729N6 Overview

2.3 Description

The BGA729N6 covers a wide frequency range from 70 MHz to 1000 MHz. The LNA provides 16.3 dB gain and 1.05 dB noise figure at a current consumption of 6.3 mA in the application configuration described in Chapter 3 of the datasheet. In bypass mode, the LNA provides an insertion loss of -4.2 dB. The bypass mode with much higher linearity enables this LNA to work with much lower current consumption than commonly used TV LNAs. The BGA729N6 is based upon Infineon Technologies's B7HF Silicon Germanium technology. It operates from 1.5 V to 3.3 V supply voltage.

Please visit the product page of **BGA729N6** for more information.




Figure 3 Equivalent Circuit of BGA729N6

Product Name	Marking	Code
BGA729N6	M	TSNP-6-2

Table 1 Pin Assignment of BGA729N6

Pin No.	Symbol	Function
1	GS	High gain / bypass control
2	VCC	DC supply
3	AO	LNA output

Table 1 Pin Assignment of BGA729N6

Pin No.	Symbol	Function
4	GND	Ground
5	AI	LNA input
6	PON	Power on / off control

Table 2 Gain Mode Selection Truth Table

Control Voltage V_{PON}	Control Voltage V_{GS}	Gain Mode
High	Low	High Gain
High	High	Bypass
Low	High	Bypass
Low	Low	Off

3 Application Circuit and Performance Overview

In this chapter the performance of the application circuit, the schematic and bill-on-materials are presented.

Device: BGA729N6
Application: Broadband LNA for Mobile TV and FM Radio Applications
PCB Marking: M150901
EVB Order No.: AN505

3.1 Summary of Measurement Results

The performance of BGA729N6 for Mobile TV and FM Radio Applications is summarized in the following table.

Table 3 Electrical Characteristics (at room temperature) for High Gain Mode

$V_{PON} = 2.8V$, $V_{BP} = 0V$

Parameter	Symbol	Value			Unit	Comment/Test Condition
Application System	Sys	FM Radio	MobileTV UHF	MobileTV UHF	MHz	
DC Voltage	Vcc	2.8			V	
DC Current	Icc	7.0			mA	
Frequency Range	Freq	98 ¹⁾	202	715	MHz	
Insertion Power Gain	G	17.5	17.3	16.1	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Noise Figure	NF	0.95	1.05	1.20	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Input Return Loss	RLin	9.8	10.3	9.6	dB	
Output Return Loss	RLout	22.1	22.9	16.5	dB	
Reverse Isolation	IRev	27.4	27.4	28.7	dB	
Input P1dB	IP1dB	-17.8	-17.6	-14.1	dBm	
Output P1dB	OP1dB	-1.3	-1.3	1	dBm	
Input IP3	IIP3	-2.4	-3.3	-3.3	dBm	f1 = 98, 202, 715 MHz respectively, f2 = f1 + 1 MHz -30 dBm per tone
Output IP3	OIP3	15.1	14.0	12.8	dBm	
Stability	k	>1			--	Measured up to 10 GHz

Note: 1) Globally the FM radio frequencies are allocated between 66 – 108 MHz.

Table 1 Electrical Characteristics (at room temperature) for Bypass Mode

$V_{PON} = 2.8V$, $V_{BP} = 2.8V$

Parameter	Symbol	Value			Unit	Comment/Test Condition
Application System	Sys	FM Radio	MobileTV UHF	MobileTV UHF	MHz	
DC Voltage	Vcc	2.8			V	
DC Current	Icc	0.6			mA	
Frequency Range	Freq	98 ¹⁾	202	715	MHz	
Gain	G	-6.4	-4.7	-4.2	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Noise Figure	NF	7.65	4.90	4.20	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Input Return Loss	RLin	5.6	10.1	15.3	dB	
Output Return Loss	RLout	11.4	13.3	12.2	dB	
Reverse Isolation	IRev	6.4	4.7	4.2	dB	
Input P1dB	IP1dB	6.1	5.3	6.0	dBm	
Output P1dB	OP1dB	-1.3	-0.4	0.8	dBm	
Input IP3	IIP3	23.2	21.2	23.8	dBm	f1 = 98, 202, 715 MHz respectively, f2 = f1 + 1 MHz -10 dBm per tone
Output IP3	OIP3	16.8	16.5	19.6	dBm	
Stability	k	>1			--	Measured up to 10 GHz

Note: 1) Globally the FM radio frequencies are allocated between 66 – 108 MHz.

Table 2 Electrical Characteristics (at room temperature) for High Gain Mode

$$V_{PON} = 1.8V, V_{BP} = 0V$$

Parameter	Symbol	Value			Unit	Comment/Test Condition
Application System	Sys	FM Radio	MobileTV UHF	MobileTV UHF	MHz	
DC Voltage	Vcc	1.8			V	
DC Current	Icc	6.9			mA	
Frequency Range	Freq	98 ¹⁾	202	715	MHz	
Insertion Power Gain	G	17.4	17.2	16.0	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Noise Figure	NF	0.95	1.05	1.20	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Input Return Loss	RLin	9.6	10.2	9.4	dB	
Output Return Loss	RLout	21.8	22.4	16.1	dB	
Reverse Isolation	IRev	27.3	27.4	28.4	dB	
Input P1dB	IP1dB	-16.4	-15.2	-15.6	dBm	
Output P1dB	OP1dB	0.0	1.0	-0.6	dBm	
Input IP ₃	IIP ₃	-3.4	-4.6	-4.0	dBm	f ₁ = 98, 202, 715 MHz respectively, f ₂ = f ₁ + 1 MHz -30 dBm per tone
Output IP ₃	OIP ₃	14.0	12.6	12.0	dBm	
Stability	k	>1			--	Measured up to 10 GHz

Note: 1) Globally the FM radio frequencies are allocated between 66 – 108 MHz.

Table 3 Electrical Characteristics (at room temperature) for Bypass Mode

$V_{PON} = 1.8V$, $V_{BP} = 1.8V$

Parameter	Symbol	Value			Unit	Comment/Test Condition
Application System	Sys	FM Radio	MobileTV UHF	MobileTV UHF	MHz	
DC Voltage	Vcc	1.8			V	
DC Current	Icc	0.3			mA	
Frequency Range	Freq	98 ¹⁾	202	715	MHz	
Insertion Power Gain	G	-6.5	-4.9	-4.5	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Noise Figure	NF	7.10	5.05	4.40	dB	Loss of input/output line of 0.01 dB@ 98MHz, 0.02 dB @ 202MHz, 0.06 dB @715 MHz are included
Input Return Loss	RLin	5.8	10.3	14.4	dB	
Output Return Loss	RLout	11.6	13.6	12.4	dB	
Reverse Isolation	IRev	6.6	5.0	4.5	dB	
Input P1dB	IP1dB	4.2	2.5	5.4	dBm	
Output P1dB	OP1dB	-3.3	-3.4	-0.1	dBm	
Input IP3	IIP3	17.5	15.5	18.2	dBm	f1 = 98, 202, 715 MHz respectively, f2 = f1 + 1 MHz -10 dBm per tone
Output IP3	OIP3	11	10.6	13.7	dBm	
Stability	k	>1			--	Measured up to 10 GHz

Note: 1) Globally the FM radio frequencies are allocated between 66 – 108 MHz.

3.2 BGA729N6 as 70 MHz – 1000 MHz Low Noise Amplifier for Mobile TV and FM Radio Applications

The BGA729N6 is a Silicon Germanium Low Noise Amplifier for mobile TV applications and FM radio application in the range from 70 MHz – 1000 MHz. In this application note, the performance of BGA729N6 for mobile TV and FM radio applications is investigated at 1.8 V and 2.8 V supply voltages. The circuit targets to use as few components as possible.

At 2.8 V, 98 MHz, in the high gain mode the BGA729N6 achieves a noise figure of 0.95 dB and a gain of 17.5 dB. The input return loss is 9.8 dB and output return loss is 22.1 dB. It obtains the input 1dB Compression Point (IP1dB) at -17.8 dBm. Using two tones of -30 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of -2.4 dBm.

At 2.8 V, 98 MHz, in the bypass mode the BGA729N6 achieves a noise figure of >3.0 dB and an insertion loss of 6.4 dB. The input return loss is 5.6 dB and output return loss is 11.4 dB. It obtains the input 1dB Compression Point (IP1dB) at 6.1 dBm. Using two tones of -10 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of 23.2 dBm.

At 2.8 V, 202 MHz, in the high gain mode the BGA729N6 achieves a noise figure of 1.05 dB and a gain of 17.3 dB. The input return loss is 10.3 dB and output return loss is 22.9 dB. It obtains the input 1dB Compression Point (IP1dB) at -17.6 dBm. Using two tones of -30 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of -3.3 dBm.

At 2.8 V, 202 MHz, in the bypass mode the BGA729N6 achieves a noise figure of >3.0 dB and an insertion loss of 4.7 dB. The input return loss is 10.1 dB and output return loss is 13.3 dB. It obtains the input 1dB Compression Point (IP1dB) at 5.3 dBm. Using two tones of -10 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of 21.2 dBm.

At 2.8 V, 715 MHz, in the high gain mode the BGA729N6 achieves a noise figure of 1.20 dB and a gain of 16.1 dB. The input return loss is 9.6 dB and output return loss is 16.5 dB. It obtains the input 1dB Compression Point (IP1dB) at -14.1 dBm. Using two tones of -30 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of -3.3 dBm.

At 2.8 V, 715 MHz, in the bypass mode the BGA729N6 achieves a noise figure of >3.0 dB and an insertion loss of 4.2 dB. The input return loss is 15.3 dB and output return loss is 12.2 dB. It obtains the input 1dB Compression Point (IP1dB) at 6.0 dBm. Using two tones of -10 dBm spacing 1 MHz, the circuit achieves an input Third-order Intercept Point (IIP3) of 23.8 dBm.

The circuit is unconditionally stable up to 10 GHz.

3.3 Schematics and Bill-of-Materials

The schematic of BGA729N6 for mobile TV and FM radio applications is presented in **Figure 4** and its bill-of-materials is shown in **Table 4**.




Figure 4 Schematics of the BGA729N6 Application Circuit

Table 4 Bill-of-Materials

Symbol	Value	Unit	Size	Manufacturer	Comment
C1	1	nF	0201	Various	DC block ¹⁾
C2	1	nF	0201	Various	DC block ¹⁾
C3	≥ 1	nF	0201	Various	RF bypass ²⁾ . Necessary in FM application, optional in mobile TV application.
N1	BGA729N6		TSNP-6-2	Infineon	SiGe LNA

Note: DC block function is NOT integrated at input of BGA729N6. The DC block capacitors C1 and C2 are not necessary if the DC block function on the RF input line can be ensured by the previous stage.

Note: The RF bypass capacitor C3 at the DC power supply pin filters out the power supply noise and stabilizes the DC supply. The RF bypass capacitor C3 is not necessary if a clean and stable DC supply can be ensured.

4 Measurement Graphs

The performance of the application circuit is presented with the following graphs.




Figure 5 Insertion Power Gain (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 6 Insertion Power Gain (High Gain, Wideband) of BGA729N6 for TV_Radio Applications




Figure 7 Noise Figure (High Gain) of BGA729N6 for TV_Radio Applications




Figure 8 Input Return Loss (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 9 Input Return Loss (High Gain, Smith Chart) of BGA729N6 for TV_Radio Applications




Figure 10 Output Return Loss (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 11 Output Return Loss (High Gain, Smith Chart) of BGA729N6 for TV_Radio Applications




Figure 12 Reverse Isolation (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 13 Stability K-factor (High Gain) of BGA729N6 for TV_Radio Applications




Figure 14 Stability μ_1 -factor (High Gain) of BGA729N6 for TV_Radio Applications




Figure 15 Stability Mu2-factor (High Gain) of BGA729N6 for TV_Radio Applications




Figure 16 Input 1dB Compression Point (High Gain, 1.8 V) of BGA729N6 for TV_Radio Applications




Figure 17 Input 1dB Compression Point (High Gain, 2.8 V) of BGA729N6 for TV_Radio Applications




Figure 18 Third-order Interception Point (High Gain, 1.8 V) of BGA729N6 for TV_Radio Applications




Figure 19 Third-order Interception Point (High Gain, 2.8 V) of BGA729N6 for TV_Radio Applications




Figure 20 Insertion Power Gain (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 21 Insertion Power Gain (Bypass, Wideband) of BGA729N6 for TV_Radio Applications




Figure 22 Noise Figure (Bypass) of BGA729N6 for TV_Radio Applications




Figure 23 Input Return Loss (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 24 Input Return Loss (Bypass, Smith Chart) of BGA729N6 for TV_Radio Applications




Figure 25 Output Return Loss (Bypass, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 26 Output Return Loss (Bypass, Smith Chart) of BGA729N6 for TV_Radio Applications




Figure 27 Reverse Isolation (High Gain, Narrowband) of BGA729N6 for TV_Radio Applications




Figure 28 Stability K-factor (Bypass) of BGA729N6 for TV_Radio Applications




Figure 29 Stability μ_1 -factor (Bypass) of BGA729N6 for TV_Radio Applications




Figure 30 Stability μ_2 -factor (Bypass) of BGA729N6 for TV_Radio Applications




Figure 31 Input 1dB Compression Point (Bypass, 1.8 V) of BGA729N6 for TV_Radio Applications




Figure 32 Input 1dB Compression Point (Bypass, 2.8 V) of BGA729N6 for TV_Radio Applications




Figure 33 Third-order Interception Point (Bypass, 1.8 V) of BGA729N6 for TV_Radio Applications




Figure 34 Third-order Interception Point (Bypass, 2.8 V) of BGA729N6 for TV_Radio Applications

5 Evaluation Board and Layout Information

In this application note, the following PCB is used:

PCB Marking: **M150901**

PCB material: **<FR4>**

ϵ_r of PCB material: **<4.8>**




Figure 35 Photo Picture of Evaluation Board (overview) <PCB Marking M150901 Rev.1.0>




Figure 36 Photo Picture of Evaluation Board (detailed view)

Broadband MMIC: BGA729N6

Low Noise Amplifier for Portable and Mobile TV Applications and FM Radio

Evaluation Board and Layout Information




Figure 37 PCB Layer Information

6 Authors

Mark Schmidt, Working Student of Business Unit "RF and Sensor Devices"

Xiang Li, Application Engineer of Business Unit "RF and Sensor Devices"

7 Reference

- [1] Application Guide for Mobile Communications 2015, Infineon Technologies, Business Unit RF and Sensors
- [2] https://en.wikipedia.org/wiki/FM_broadcasting
- [3] FM broadcasting frequencies: most of the countries transmit FM signals between 87.5 MHz – 108 MHz; a few other countries transmit FM signals at 66 MHz – 74 MHz and 76 MHz – 90 MHz.
http://www.itu.int/dms_pubrec/itu-r/rec/bs/R-REC-BS.450-3-200111-I!!PDF-E.pdf

Revision History

Major changes since the last revision

Page or Reference	Description of change

Trademarks of Infineon Technologies AG

μHVIC™, μIPM™, μPFC™, AU-ConvertIR™, AURIX™, C166™, CanPAK™, CIPOS™, CIPURSE™, CoolDP™, CoolGaN™, COOLiR™, CoolMOS™, CoolSET™, CoolSiC™, DAVE™, DI-POL™, DirectFET™, DrBlade™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPACK™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, GaNpowIR™, HEXFET™, HITFET™, HybridPACK™, iMOTION™, IRAM™, ISOFACE™, IsoPACK™, LEDriviR™, LITIX™, MIPAQ™, ModSTACK™, my-d™, NovalithiC™, OPTIGA™, OptiMOS™, ORIGA™, PowIRaudio™, PowIRStage™, PrimePACK™, PrimeSTACK™, PROFET™, PRO-SiL™, RASIC™, REAL3™, SmartLEWIS™, SOLID FLASH™, SPOC™, StrongIRFET™, SupIRBuck™, TEMPFET™, TRENCHSTOP™, TriCore™, UHVIC™, XHP™, XMC™

Trademarks updated November 2015

Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2016-11-o8

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2016 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

AN_2016_09_PL32_004

IMPORTANT NOTICE

The information contained in this application note is given as a hint for the implementation of the product only and shall in no event be regarded as a description or warranty of a certain functionality, condition or quality of the product. Before implementation of the product, the recipient of this application note must verify any function and other technical information given herein in the real application. Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind (including without limitation warranties of non-infringement of intellectual property rights of any third party) with respect to any and all information given in this application note.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.