

INTELLIGENT POWER LOW SIDE SWITCH

Features

- Over temperature shutdown
- Over current shutdown
- Active clamp
- Low current & logic level input
- ESD protection
- Optimized Turn On/Off for EMI
- Diagnostic on the input current

Applications

- Solenoids and relays
- 24V truck loads

Description

The AUIPS2051L/AUIPS2052G is a three terminal Intelligent Power Switch (IPS) that features a low side MOSFET with over-current, over-temperature, ESD protection and drain to source active clamp. The AUIPS2052 is a dual channel device while the AUIPS2051 is a single channel. This device offers protections and the high reliability required in harsh environments. The switch provides efficient protection by turning OFF the power MOSFET when the temperature exceeds 165°C or when the drain current reaches 1.8A. The device restarts once the input is cycled. A serial resistance connected to the input provides the diagnostic. The avalanche capability is significantly enhanced by the active clamp and covers most inductive load demagnetizations.

Product Summary

 $\begin{array}{ll} \text{Rds(on)} & 300\text{m}\Omega \text{ (max.)} \\ \text{Vclamp} & 70\text{V} \\ \text{Ishutdown} & 1.8\text{A (typ.)} \end{array}$


Packages





SOT223 AUIPS2051L SO-8 AUIPS2052G

Typical Connection



International IOR Rectifier

AUIPS2051L/AUIPS2052G

Qualification Information[†]

| Qualification information | | | | | | |
|---------------------------|-------------------|---|--|--|--|--|
| | | | Automotive (per AEC-Q100 ^{††}) | | | |
| Qualification Level | | Industrial and Consumer | Comments: This IC has passed an Automotive qualification. IR's Industrial and Consumer qualification level is granted by extension of the higher Automotive level. | | | |
| | | SOT-223 | MSL2 ^{††} , 260°C (per IPC/JEDEC J-STD-020) | | | |
| Moisture 3 | Sensitivity Level | 8L-SOICN MSL2 ^{††} , 260°C (per IPC/JEDEC J-STD-020) | | | | |
| | Machine Model | (| Class M3 (per AEC-Q-100-003) | | | |
| ESD Human Body Model | | (| Class H2 (per AEC-Q-100-002) | | | |
| Charged Device Model | | Class C5 (per AEC-Q-100-011) | | | | |
| IC Latch-U | p Test | | ClassII, Level A (per AEC-Q100-004) | | | |
| RoHS Com | npliant | Yes | | | | |

Qualification standards can be found at International Rectifier's web site http://www.irf.com/

[†] †† Exceptions to AEC-Q100 requirements are noted in the qualification report.

Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters

are referenced to Ground lead. (Tambient=25°C unless otherwise specified).

| Symbol | Parameter | Min. | Max. | Units |
|-----------|---|------|------|-------|
| Vds | Maximum drain to source voltage | | 60 | V |
| Vds cont. | Maximum continuous drain to source voltage | - | 35 | V |
| Vin | Maximum input voltage | -0.3 | 6 | V |
| Isd cont. | Max diode continuous current (limited by thermal dissipation) Rth=125°C/W | _ | 1 | Α |
| Pd | Maximum power dissipation (internally limited by thermal protection) Rth=60C°/W AUIPS2051L 1" sqr. footprint | | 2 | W |
| | Rth=100°C/W AUIPS2052G std. footprint | _ | 1.25 | |
| | Electrostatic discharge voltage (Human body) C=100pF, R=1500Ω | | | |
| | Between drain and source | _ | 4 | |
| ESD | Other combinations | | 3 | kV |
| ESD | Electrostatic discharge voltage (Machine Model) C=200pF,R=0Ω | | | ΚV |
| | Between drain and source | _ | 0.5 | |
| | Other combinations | | 0.3 | |
| Tj max. | Max. storage & operating temperature junction temperature | -40 | 150 | °C |

Thermal Characteristics

| Symbol | Parameter | Тур. | Max. | Units | |
|--------|--|------|------|-------|--|
| Rth1 | Thermal resistance junction to ambient SOT-223 std. footprint | | _ | | |
| Rth2 | Thermal resistance junction to ambient SOT-223 1" sqr. footprint | | _ | | |
| Rth1 | Thermal resistance junction to ambient SO-8 std. Footprint | | | °C/W | |
| Kuii | 1 die active | 100 | | C/VV | |
| Rth1 | Thermal resistance junction to ambient SO-8 std. footprint | 130 | | | |
| Kuii | 2 die active | | | | |

note: Tj=Power dissipated in one channel x Rth

Recommended Operating Conditions

These values are given for a quick design. For operation outside these conditions, please consult the application notes.

| Symbol | Parameter | Min. | Max. | Units |
|-------------|---|------|------|-------|
| VIH | High level input voltage | 4 | 5.5 | |
| VIL | Low level input voltage | 0 | 0.5 | |
| lds | Continuous drain current, Tambient=85°C, Tj=125°C, Vin=5V,Rth=100°C/W | _ | 0.9 | Α |
| Rin | Recommended resistor in series with IN pin to generate a diagnostic | 0.5 | 5 | kΩ |
| Max. t rise | Max. input rising time | _ | 1 | μs |

Static Electrical Characteristics

Ti=-40..150°C. Vcc=28V (unless otherwise specified)

| Symbol | Parameter | Min. | Тур. | Max. | Units | Test Conditions |
|-----------|--|------|------|------|------------|------------------------|
| Rds(on) | ON state resistance Tj=25°C | _ | 250 | 300 | ~ 0 | Vin=5V, Ids=1A |
| | ON state resistance Tj=150°C(2) | _ | 440 | 520 | mΩ | VIII=5V, IUS=1A |
| ldss1 | Drain to source leakage current | _ | 0.2 | 1 | | Vcc=28V, Tj=25°C |
| ldss2 | Drain to source leakage current | _ | 0.5 | 2 | μA | Vcc=50V, Tj=25°C |
| V clamp1 | Drain to source clamp voltage 1 | 63 | 69 | _ | | Id=20mA See fig. 3 & 4 |
| V clamp2 | Drain to source clamp voltage 2 | _ | 70 | 75 | V | ld=150mA |
| Vin clamp | IN to source pin clamp voltage | 5.5 | 6.2 | 7.5 | v | lin=1mA |
| Vth | Input threshold voltage | 1.1 | 2 | 2.7 | | Id=50mA |
| lin, on | ON state IN positive current | 15 | 40 | 80 | | Vin=5V |
| lin, off | OFF state IN positive current (after protection latched) | 150 | 250 | 350 | μA | |

Switching Electrical Characteristics Vcc=28V, Resistive load=50Ω, Rinput=50Ω, Vin=5V, Tj=25°C

| Symbol | Parameter | Min. | Тур. | Max. | Units | Test Conditions |
|------------|----------------------------|------|------|------|-------|-----------------|
| Tdon | Turn-on delay time to 20% | 0.1 | 1 | 3 | | |
| Tr | Rise time 20% to 80% | 0.1 | 0.3 | 2.5 | | See figure 2 |
| Tdoff | Turn-off delay time to 80% | 1 | 1.8 | 3.5 | μs | See ligure 2 |
| Tf | Fall time 80% to 20% | 0.1 | 0.5 | 2.5 | | |
| Eon + Eoff | Turn on and off energy | _ | 5 | _ | μJ | |

Protection Characteristics


Tj=-40..150°C, Vcc=28V (unless otherwise specified)

| Symbol | Parameter | Min. | Тур. | Max. | Units | Test Conditions |
|--------|-------------------------------|--------|------|------|-------|-----------------|
| Tsd | Over temperature threshold | 150(2) | 165 | _ | °C | See figure 1 |
| Isd | Over current threshold | 1.2 | 1.8 | 3 | Α | See figure 1 |
| Vreset | IN protection reset threshold | 1.1 | 1.6 | 2 | V | |
| Treset | Time to reset protection | 15(2) | 50 | 500 | μs | Vin=0V, Tj=25°C |


⁽²⁾ Guaranteed by design



Lead Assignments



Functional Block Diagram



International **TOR** Rectifier

AUIPS2051L/AUIPS2052G

All curves are typical values. Operating in the shaded area is not recommended.




Figure 1 - Timing diagram




Figure 2 - IN rise time & switching definitions




Figure 3 - Active clamp waveforms




Figure 4 - Active clamp test circuit




Figure 5 - Normalized Rdson (%) Vs Input voltage (V)

Figure 6 - Normalized Rds(on) (%) Vs Tj (°C)




Figure 7 – Current limitation and current shutdown Vs Input voltage (V)




Figure 8 – Normalized I shutdown (%) Vs junction temperature (°C)




Figure 9 – Max. continuous output current (A) Vs Ambient temperature (°C)

Figure 10 – Idss1 (μA) Vs temperature (°C)




Figure 11 – Max. ouput current (A)
Vs Inductive load (mH)





Figure 12 – Transient thermal impedance (°C/W)
Vs time (s)

This is for single pulse when Tj=165°C and for repetitive pulses when Tj<115°C before turning off.

International **TOR** Rectifier

AUIPS2051L/AUIPS2052G




Tsd, over temperature shutdown (°C) Vin, input voltage (V)

Figure 13 – Input current (μA) On and Off Vs junction temperature (°C)

Figure 14 – Over temperature shutdown (°C)
Vs input voltage (V)



Case Outline - SOT-223





| POS | MILLIM | ETERS | INC | HES |
|------------------|--------|-------|-----------|--------|
| 1 | MAX | MIN | MAX | MIN |
| A | 1.70 | 1.50 | .067 | .060 |
| A1 | 0.10 | 0.02 | .004 | .0008 |
| B B1 | 3.15 | 2.95 | .124 | .116 |
| B1 | 0.85 | 0.65 | .033 | .026 |
| C | 0.35 | 0.25 | .014 | .010 |
| D | 6.70 | 6.30 | .264 | .248 |
| е | 2.30 | NOM | .0905 NOM | |
| e1 E | 4.60 | NOM | .181 | NOM |
| E | 3.70 | 3.30 | .146 | .130 |
| H S t O | 7.30 | 6.70 | .287 | .264 |
| S | 1.05 | 0.85 | .041 | .033 |
| t | 1.30 | 1.10 | .051 | .043 |
| Θ | 10° k | (AX | 10° | MAX |
| Θ1 | 16° | 10° | 16° | 10° |
| Θ2 | 16* | 10° | 16* | 10° |
| L | 0.75 | MIN | 0.02 | 95 MIN |

- NOTE:

 1. PACKAGE OUTLINE EXCLUSIVE OF ANY MOLD FLASHES DIMENSION.

 2. PACKAGE OUTLINE EXCLUSIVE OF BURR DIMENSION.






Leads and drain are plated with 100% Sn

International Rectifier

AUIPS2051L/AUIPS2052G


Tape & Reel - SOT-223

Dimensions are shown in milimeters (inches)




NOTES:

- 1. CONTROLLING DIMENSION: MILLIMETER.
- 2. OUTLINE CONFORMS TO EIA-481 & EIA-541.
- 3. EACH \$\oldsymbol{\psi}330.00 (13.00) REEL CONTAINS 2,500 DEVICES.






- 1. OUTLINE COMFORMS TO EIA-418-1.
- 2. CONTROLLING DIMENSION: MILLIMETER..
- DIMENSION MEASURED @ HUB.
- INCLUDES FLANGE DISTORTION @ OUTER EDGE.




Case Outline - SO-8

Dimensions are shown in millimeters (inches)




| P P P | C |
|-----------------------|-------------|
| | 0.10 (.004) |
| → 8X b A1 | 0.10 (.004) |
| ⊕ 0.25 (.010) M C A B | |

| DIM | INC | HES | MILLIN | /IETERS |
|--------|---------|-------|--------|---------|
| וועווע | MIN | MAX | MIN | MAX |
| Α | .0532 | .0688 | 1.35 | 1.75 |
| A1 | .0040 | .0098 | 0.10 | 0.25 |
| b | .013 | .020 | 0.33 | 0.51 |
| С | .0075 | .0098 | 0.19 | 0.25 |
| D | .189 | .1968 | 4.80 | 5.00 |
| Ε | .1497 | .1574 | 3.80 | 4.00 |
| е | .050 B. | ASIC | 1.27 E | BASIC |
| e1 | .025 B | ASIC | 0.635 | BASIC |
| Н | .2284 | .2440 | 5.80 | 6.20 |
| K | .0099 | .0196 | 0.25 | 0.50 |
| L | .016 | .050 | 0.40 | 1.27 |
| У | 0° | 8° | 0° | 8° |




NOTES:

- 1. DIMENSIONING & TOLERANGING PER ASME Y14.5M-1994.
- 2. CONTROLLING DIMENSION: MILLIMETER
- 3. DIMENSIONS ARE SHOWN IN MILLIMETERS (INCHES).
- 4. OUTLINE CONFORMS TO JEDEC OUTLINE MS-012AA.
- (5) DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.15 (.006).
- (6) DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.25 (.010).
- DIMENSION IS THE LENGTH OF LEAD FOR SOLDERINGTO A SUBSTRATE.



Leads and drain are plated with 100% Sn

Tape & Reel - SO-8



Notes:


- 1. 10 sprocket hole pitch cumulative tolerance 0.2
- Camber not to exceed 1mm in 100mm
- Material: Black Conductive Advantek Polystyrene
 Ao and Bo measured on a plane 0.3mm above the bottom of the pocket
- 5. Ko measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- 6. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.


Ao = 6.4 mm Bo = 5.2 mm

Ko = 2.1 mm

- All Dimensions in Millimeters -

Part Marking Information





Ordering Information

| Base Part Number | | Standard Pack | 0 14 5 44 1 | |
|----------------------|--------------|---------------|-------------|----------------------|
| base i ait ivuilibei | Package Type | Form | Quantity | Complete Part Number |
| ALUD920541 | SOT223 | Tube | 80 | AUIPS2051L |
| AUIPS2051L | 501223 | Tape and reel | 2500 | AUIPS2051LTR |
| ALUD000500 | 500 | Tube | 95 | AUIPS2052G |
| AUIPS2052G | SO8 | Tape and reel | 2500 | AUIPS2052GTR |

International Rectifier

AUIPS2051L/AUIPS2052G

IMPORTANT NOTICE

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

IR products are neither designed nor intended for use in military/aerospace applications or environments unless the IR products are specifically designated by IR as military-grade or "enhanced plastic." Only products designated by IR as military-grade meet military specifications. Buyers acknowledge and agree that any such use of IR products which IR has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

IR products are neither designed nor intended for use in automotive applications or environments unless the specific IR products are designated by IR as compliant with ISO/TS 16949 requirements and bear a part number including the designation "AU". Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, IR will not be responsible for any failure to meet such requirements.

For technical support, please contact IR's Technical Assistance Center http://www.irf.com/technical-info/

WORLD HEADQUARTERS:

101 N Sepulbeda Blvd., El Segundo, California 90245 Tel: (310) 252-7105

International **TOR** Rectifier

AUIPS2051L/AUIPS2052G

Revision History

| Revision | Date | Notes/Changes |
|----------|---------------------------------|--|
| Α | 30/10/08 | First release |
| В | 23/03/2009 | Add latch up information |
| С | 15/09/2009 | Add application section |
| D | 21/02/2011 | Update Fig 11 |
| E | November, 14 th 2011 | Update T&R SOT223 |
| F | May 9 th , 2012 | Update the component number of the SOT223 tube |
| | | |
| | | |
| | | |