


Final datasheet

EasyPIM™ module with TRENCHSTOP™ IGBT7 and emitter controlled 7 diode and NTC

Features

- Electrical features
 - $V_{CES} = 1200\text{ V}$
 - $I_{C\text{ nom}} = 35\text{ A} / I_{CRM} = 70\text{ A}$
 - TRENCHSTOP™ IGBT7
 - Overload operation up to 175°C
 - Low $V_{CE,sat}$
 - Suitable Infineon gate drivers can be found under <https://www.infineon.com/gdfinder>
- Mechanical features
 - Al_2O_3 substrate with low thermal resistance
 - Solder contact technology
 - High power density
 - Compact design
 - 2.5 kV AC 1 minute insulation



Potential applications

- Air conditioning
- Auxiliary inverters
- Motor drives

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	Diode, Rectifier	6
5	IGBT, Brake-Chopper	7
6	Diode, Brake-Chopper	8
7	NTC-Thermistor	9
8	Characteristics diagrams	11
9	Circuit diagram	17
10	Package outlines	18
11	Module label code	19
	Revision history	20
	Disclaimer	21

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	2.5	kV
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Comparative tracking index	CTI		> 200	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{SCE}			30		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_H = 25 \text{ °C}$, per switch		6		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25 \text{ °C}$, per switch		5		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting force per clamp	F		40		80	N
Weight	G			39		g

Note: The current under continuous operation is limited to 30 A rms per connector pin.

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25 \text{ °C}$	1200	V
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 175 \text{ °C}$	$T_H = 105 \text{ °C}$	35	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj \text{ op}}$		70	A
Gate-emitter peak voltage	V_{GES}			±20	V

Table 4 **Characteristic values**

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 35\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$		1.60	1.85	V
			$T_{vj} = 125\ ^\circ C$		1.74		
			$T_{vj} = 175\ ^\circ C$		1.82		
Gate threshold voltage	V_{GETh}	$I_C = 0.75\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$		5.15	5.8	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 600\ V, T_{vj} = 25\ ^\circ C$			0.548		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$			0.0		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			6.62		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			0.023		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$			0.0058	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$				100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 35\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 5.6\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.037		μs
			$T_{vj} = 125\ ^\circ C$		0.043		
			$T_{vj} = 175\ ^\circ C$		0.044		
Rise time (inductive load)	t_r	$I_C = 35\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Gon} = 5.6\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.035		μs
			$T_{vj} = 125\ ^\circ C$		0.037		
			$T_{vj} = 175\ ^\circ C$		0.038		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 35\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 5.6\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.260		μs
			$T_{vj} = 125\ ^\circ C$		0.320		
			$T_{vj} = 175\ ^\circ C$		0.340		
Fall time (inductive load)	t_f	$I_C = 35\ A, V_{CC} = 600\ V, V_{GE} = \pm 15\ V, R_{Goff} = 5.6\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.140		μs
			$T_{vj} = 125\ ^\circ C$		0.240		
			$T_{vj} = 175\ ^\circ C$		0.300		
Turn-on energy loss per pulse	E_{on}	$I_C = 35\ A, V_{CC} = 600\ V, L_\sigma = 35\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 5.6\ \Omega, di/dt = 700\ A/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		2.62		mJ
			$T_{vj} = 125\ ^\circ C$		3.73		
			$T_{vj} = 175\ ^\circ C$		4.45		
Turn-off energy loss per pulse	E_{off}	$I_C = 35\ A, V_{CC} = 600\ V, L_\sigma = 35\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 5.6\ \Omega, dv/dt = 3300\ V/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		2.39		mJ
			$T_{vj} = 125\ ^\circ C$		3.73		
			$T_{vj} = 175\ ^\circ C$		4.56		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}$, $V_{CC} = 800 \text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$		110		A
				100		
Thermal resistance, junction to heat sink	R_{thJH}	per IGBT, $\lambda_{grease} = 4.3 \text{ W/(m} \cdot \text{K)}$		0.931		K/W
Temperature under switching conditions	$T_{vj op}$		-40		175	°C

Note: $T_{vj op} > 150^\circ\text{C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25^\circ\text{C}$	1200	V
Continuous DC forward current	I_F		35	A
Repetitive peak forward current	I_{FRM}	$t_P = 1 \text{ ms}$	70	A
I^2t - value	I^2t	$t_P = 10 \text{ ms}$, $V_R = 0 \text{ V}$	$T_{vj} = 125^\circ\text{C}$	A^2s
			$T_{vj} = 175^\circ\text{C}$	

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 35 \text{ A}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25^\circ\text{C}$	1.72	2.10	V
			$T_{vj} = 125^\circ\text{C}$	1.59		
			$T_{vj} = 175^\circ\text{C}$	1.52		
Peak reverse recovery current	I_{RM}	$V_{CC} = 600 \text{ V}$, $I_F = 35 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 700 \text{ A}/\mu\text{s}$ ($T_{vj} = 175^\circ\text{C}$)	$T_{vj} = 25^\circ\text{C}$	22.4		A
			$T_{vj} = 125^\circ\text{C}$	29.6		
			$T_{vj} = 175^\circ\text{C}$	34		

(table continues...)

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_r	$V_{CC} = 600\text{ V}$, $I_F = 35\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 700\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	2.46		μC
			$T_{vj} = 125\text{ °C}$	4.8		
			$T_{vj} = 175\text{ °C}$	6.52		
Reverse recovery energy	E_{rec}	$V_{CC} = 600\text{ V}$, $I_F = 35\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 700\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	1.12		mJ
			$T_{vj} = 125\text{ °C}$	2.02		
			$T_{vj} = 175\text{ °C}$	2.63		
Thermal resistance, junction to heat sink	R_{thJH}	per diode, $\lambda_{grease} = 4.3\text{ W}/(\text{m}\cdot\text{K})$		1.34		K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	°C

Note: $T_{vj\text{ op}} > 150\text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

4 Diode, Rectifier

Table 7 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25\text{ °C}$	1600	V
Maximum RMS forward current per chip	I_{FRMSM}	$T_H = 100\text{ °C}$		45	A
Maximum RMS current at rectifier output	I_{RMSM}	$T_H = 100\text{ °C}$		50	A
Surge forward current	I_{FSM}	$t_p = 10\text{ ms}$	$T_{vj} = 25\text{ °C}$	450	A
			$T_{vj} = 150\text{ °C}$	370	
I^2t - value	I^2t	$t_p = 10\text{ ms}$	$T_{vj} = 25\text{ °C}$	1010	A ² s
			$T_{vj} = 150\text{ °C}$	685	

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 35\text{ A}$ $T_{vj} = 150\text{ °C}$		0.95		V
Reverse current	I_r	$T_{vj} = 150\text{ °C}$, $V_R = 1600\text{ V}$		1		mA
Thermal resistance, junction to heat sink	R_{thJH}	per diode, $\lambda_{grease} = 4.3\text{ W}/(\text{m}\cdot\text{K})$		1.18		K/W

(table continues...)

Table 8 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Temperature under switching conditions	$T_{vj, op}$		-40		150	°C

5 IGBT, Brake-Chopper

Table 9 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25\text{ °C}$	1200	V
Continuous DC collector current	I_{CDC}	$T_{vj\ max} = 175\text{ °C}$	$T_H = 105\text{ °C}$	35	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$		70	A
Gate-emitter peak voltage	V_{GES}			±20	V

Table 10 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 35\text{ A}$, $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$		1.60	1.85	V
			$T_{vj} = 125\text{ °C}$		1.74		
			$T_{vj} = 175\text{ °C}$		1.82		
Gate threshold voltage	V_{GETh}	$I_C = 0.75\text{ mA}$, $V_{CE} = V_{GE}$, $T_{vj} = 25\text{ °C}$		5.15	5.8	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15\text{ V}$, $V_{CC} = 600\text{ V}$, $T_{vj} = 25\text{ °C}$			0.548		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\text{ °C}$			0.0		Ω
Input capacitance	C_{ies}	$f = 100\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$			6.62		nF
Reverse transfer capacitance	C_{res}	$f = 100\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$			0.023		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$			0.0039	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\text{ V}$, $V_{GE} = 20\text{ V}$, $T_{vj} = 25\text{ °C}$				100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 35\text{ A}$, $V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 5.6\text{ Ω}$	$T_{vj} = 25\text{ °C}$		0.035		μs
			$T_{vj} = 125\text{ °C}$		0.041		
			$T_{vj} = 175\text{ °C}$		0.043		

(table continues...)

Table 10 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rise time (inductive load)	t_r	$I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Gon} = 5.6 \Omega$	$T_{vj} = 25 \text{ °C}$	0.037		μs
			$T_{vj} = 125 \text{ °C}$	0.038		
			$T_{vj} = 175 \text{ °C}$	0.041		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Goff} = 5.6 \Omega$	$T_{vj} = 25 \text{ °C}$	0.250		μs
			$T_{vj} = 125 \text{ °C}$	0.310		
			$T_{vj} = 175 \text{ °C}$	0.330		
Fall time (inductive load)	t_f	$I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Goff} = 5.6 \Omega$	$T_{vj} = 25 \text{ °C}$	0.110		μs
			$T_{vj} = 125 \text{ °C}$	0.210		
			$T_{vj} = 175 \text{ °C}$	0.270		
Turn-on energy loss per pulse	E_{on}	$I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $L_\sigma = 35 \text{ nH}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Gon} = 5.6 \Omega$, $di/dt = 700 \text{ A}/\mu\text{s}$ ($T_{vj} = 175 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$	2.53		mJ
			$T_{vj} = 125 \text{ °C}$	3.47		
			$T_{vj} = 175 \text{ °C}$	4.21		
Turn-off energy loss per pulse	E_{off}	$I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $L_\sigma = 35 \text{ nH}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Goff} = 5.6 \Omega$, $dv/dt = 3300 \text{ V}/\mu\text{s}$ ($T_{vj} = 175 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$	2.41		mJ
			$T_{vj} = 125 \text{ °C}$	3.74		
			$T_{vj} = 175 \text{ °C}$	4.58		
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}$, $V_{CC} = 800 \text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_p \leq 8 \mu\text{s}$, $T_{vj} = 150 \text{ °C}$	110		A
			$t_p \leq 7 \mu\text{s}$, $T_{vj} = 175 \text{ °C}$	100		
Thermal resistance, junction to heat sink	R_{thJH}	per IGBT, $\lambda_{grease} = 4.3 \text{ W}/(\text{m} \cdot \text{K})$		0.938		K/W
Temperature under switching conditions	$T_{vj op}$		-40		175	°C

Note: $T_{vj op} > 150 \text{ °C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

6 Diode, Brake-Chopper

Table 11 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25 \text{ °C}$	1200	V
Continuous DC forward current	I_F		10	A

(table continues...)

Table 11 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak forward current	I_{FRM}	$t_P = 1 \text{ ms}$	20	A
I^2t - value	I^2t	$t_P = 10 \text{ ms}, V_R = 0 \text{ V}$	$T_{vj} = 125^\circ\text{C}$	A^2s
			$T_{vj} = 175^\circ\text{C}$	

Table 12 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 10 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25^\circ\text{C}$	1.72	2.10	V
			$T_{vj} = 125^\circ\text{C}$	1.59		
			$T_{vj} = 175^\circ\text{C}$	1.52		
Peak reverse recovery current	I_{RM}	$V_{CC} = 600 \text{ V}, I_F = 10 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 500 \text{ A}/\mu\text{s} (T_{vj} = 175^\circ\text{C})$	$T_{vj} = 25^\circ\text{C}$	9.83		A
			$T_{vj} = 125^\circ\text{C}$	14.7		
			$T_{vj} = 175^\circ\text{C}$	16.1		
Recovered charge	Q_r	$V_{CC} = 600 \text{ V}, I_F = 10 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 500 \text{ A}/\mu\text{s} (T_{vj} = 175^\circ\text{C})$	$T_{vj} = 25^\circ\text{C}$	0.93		μC
			$T_{vj} = 125^\circ\text{C}$	1.66		
			$T_{vj} = 175^\circ\text{C}$	2.13		
Reverse recovery energy	E_{rec}	$V_{CC} = 600 \text{ V}, I_F = 10 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 500 \text{ A}/\mu\text{s} (T_{vj} = 175^\circ\text{C})$	$T_{vj} = 25^\circ\text{C}$	0.26		mJ
			$T_{vj} = 125^\circ\text{C}$	0.51		
			$T_{vj} = 175^\circ\text{C}$	0.73		
Thermal resistance, junction to heat sink	R_{thJH}	per diode, $\lambda_{grease} = 4.3 \text{ W}/(\text{m}\cdot\text{K})$		2.34		K/W
Temperature under switching conditions	$T_{vj op}$		-40		175	$^\circ\text{C}$

Note: $T_{vj op} > 150^\circ\text{C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

7 NTC-Thermistor

Table 13 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25^\circ\text{C}$		5		k Ω
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100^\circ\text{C}, R_{100} = 493 \Omega$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25^\circ\text{C}$			20	mW

(table continues...)

Table 13 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15 \text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15 \text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15 \text{ K}))]$		3433		K


Note: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4.

8 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 175\text{ °C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Gate charge characteristic (typical), IGBT, Inverter


$V_{GE} = f(Q_G)$

$I_C = 35\text{ A}, T_{vj} = 25\text{ °C}$




Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$
 $f = 100 \text{ kHz}$, $V_{GE} = 0 \text{ V}$, $T_{vj} = 25 \text{ }^{\circ}\text{C}$




Switching times (typical), IGBT, Inverter

$t = f(I_C)$
 $R_{Goff} = 5.6 \text{ }\Omega$, $R_{Gon} = 5.6 \text{ }\Omega$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 175 \text{ }^{\circ}\text{C}$




Switching times (typical), IGBT, Inverter

$t = f(R_G)$
 $I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 175 \text{ }^{\circ}\text{C}$



Voltage slope (typical), IGBT, Inverter


$dv/dt = f(R_G)$
 $I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 25 \text{ }^{\circ}\text{C}$



8 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(I_C)$
 $R_{Goff} = 5.6 \Omega$, $R_{Gon} = 5.6 \Omega$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$




Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $I_C = 35 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 5.6 \Omega$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 175 \text{ °C}$




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$




Forward characteristic (typical), Diode, Inverter

$I_F = f(V_F)$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $R_{Gon} = 5.6\ \Omega, V_{CC} = 600\ \text{V}$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $I_F = 35\ \text{A}, V_{CC} = 600\ \text{V}$




Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$




Forward characteristic (typical), Diode, Rectifier

$I_F = f(V_F)$



Transient thermal impedance, Diode, Rectifier


$Z_{th} = f(t)$



Output characteristic (typical), IGBT, Brake-Chopper


$I_C = f(V_{CE})$

$V_{GE} = 15\text{ V}$




Forward characteristic (typical), Diode, Brake-Chopper

$I_F = f(V_F)$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



9 **Circuit diagram**




Figure 1

10 Package outlines




Figure 2

11 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
	 71549142846550549911530	 71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
V2.0	2020-05-12	Preliminary datasheet
n/a	2020-09-01	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.00	2025-04-29	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-04-29

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2025 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAJ677-002

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.