

# Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as "Cypress" document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

## **Continuity of document content**

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

# **Continuity of ordering part numbers**

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

www.infineon.com



# F<sup>2</sup>MC-16FX 16-Bit Proprietary Microcontroller

CY96690 series is based on Cypress advanced  $F^2MC-16FX$  architecture (16-bit with instruction pipeline for RISC-like performance). The CPU uses the same instruction set as the established  $F^2MC-16LX$  family thus allowing for easy migration of  $F^2MC-16LX$  Software to the new  $F^2MC-16FX$  products.  $F^2MC-16FX$  product improvements compared to the previous generation include significantly improved performance - even at the same operation frequency, reduced power consumption and faster start-up time.

For high processing speed at optimized power consumption an internal PLL can be selected to supply the CPU with up to 32MHz operation frequency from an external 4MHz to 8MHz resonator. The result is a minimum instruction cycle time of 31.2ns going together with excellent EMI behavior. The emitted power is minimized by the on-chip voltage regulator that reduces the internal CPU voltage. A flexible clock tree allows selecting suitable operation frequencies for peripheral resources independent of the CPU speed.

#### **Features**

#### **Technology**

■ 0.18µm CMOS

### **CPU**

- F<sup>2</sup>MC-16FX CPU
- Optimized instruction set for controller applications (bit, byte, word and long-word data types, 23 different addressing modes, barrel shift, variety of pointers)
- 8-byte instruction queue
- Signed multiply (16-bit × 16-bit) and divide (32-bit/16-bit) instructions available

### System Clock

- On-chip PLL clock multiplier (×1 to ×8, ×1 when PLL stop)
- 4MHz to 8MHz crystal oscillator (maximum frequency when using ceramic resonator depends on Q-factor)
- Up to 8MHz external clock for devices with fast clock input feature
- 32.768kHz subsystem quartz clock
- 100kHz/2MHz internal RC clock for quick and safe startup, clock stop detection function, watchdog
- Clock source selectable from mainclock oscillator, subclock oscillator and on-chip RC oscillator, independently for CPU and 2 clock domains of peripherals
- The subclock oscillator is enabled by the Boot ROM program controlled by a configuration marker after a Power or External reset
- Low Power Consumption 13 operating modes (different Run, Sleep, Timer, Stop modes)

## **On-Chip Voltage Regulator**

■ Internal voltage regulator supports a wide MCU supply voltage range (Min=2.7V), offering low power consumption

### **Low Voltage Detection Function**

 Reset is generated when supply voltage falls below programmable reference voltage

## **Code Security**

■ Protects Flash Memory content from unintended read-out

#### **DMA**

 Automatic transfer function independent of CPU, can be assigned freely to resources

#### Interrupts

- Fast Interrupt processing
- 8 programmable priority levels
- Non-Maskable Interrupt (NMI)

#### CAN

- Supports CAN protocol version 2.0 part A and B
- ISO16845 certified
- Bit rates up to 1Mbps
- 32 message objects
- Each message object has its own identifier mask
- Programmable FIFO mode (concatenation of message objects)
- Maskable interrupt
- Disabled Automatic Retransmission mode for Time Triggered CAN applications
- Programmable loop-back mode for self-test operation

#### IISART

- Full duplex USARTs (SCI/LIN)
- Wide range of baud rate settings using a dedicated reload timer
- Special synchronous options for adapting to different synchronous serial protocols



- LIN functionality working either as master or slave LIN device.
- Extended support for LIN-Protocol (with 16-byte FIFO for selected channels) to reduce interrupt load.

#### I<sup>2</sup>C

- Up to 400kbps
- Master and Slave functionality, 7-bit and 10-bit addressing

#### A/D Converter

- SAR-type
- 8/10-bit resolution
- Signals interrupt on conversion end, single conversion mode, continuous conversion mode, stop conversion mode, activation by software, external trigger, reload timers and PPGs
- Range Comparator Function
- Scan disable Function
- ADC Pulse Detection Function

#### **Source Clock Timers**

■ Three independent clock timers (23-bit RC clock timer, 23-bit Main clock timer, 17-bit Sub clock timer)

## **Hardware Watchdog Timer**

- Hardware watchdog timer is active after reset
- Window function of Watchdog Timer is used to select the lower window limit of the watchdog interval

#### **Reload Timers**

- 16-bit wide
- Prescaler with 1/2¹, 1/2², 1/2³, 1/2⁴, 1/2⁵, 1/2⁶ of peripheral clock frequency
- Event count function

### Free-Running Timers

- Signals an interrupt on overflow, supports timer clear upon match with Output Compare (0, 4)
- Prescaler with 1, 1/2¹, 1/2², 1/2³, 1/2⁴, 1/2⁵, 1/2⁶, 1/2⁻, 1/2⁶ of peripheral clock frequency

## **Input Capture Units**

- 16-bit wide
- Signals an interrupt upon external event
- Rising edge, Falling edge or Both (rising & falling) edges sensitive

## **Output Compare Units**

- 16-bit wide
- Signals an interrupt when a match with Free-running Timer
- A pair of compare registers can be used to generate an output signal

#### **Programmable Pulse Generator**

- 16-bit down counter, cycle and duty setting registers
- Can be used as 2 x8-bit PPG
- Interrupt at trigger, counter borrow and/or duty match
- PWM operation and one-shot operation
- Internal prescaler allows 1, 1/4, 1/16, 1/64 of peripheral clock as counter clock or of selected Reload timer underflow as clock input
- Can be triggered by software or reload timer
- Can trigger ADC conversion
- Timing point capture
- Start delay

## **Stepping Motor Controller**

- Stepping Motor Controller with integrated high current output drivers
- Four high current outputs for each channel
- Two synchronized 8/10-bit PWMs per channel
- Internal prescaling for PWM clock: 1, 1/4, 1/5, 1/6, 1/8, 1/10, 1/12, 1/16 of peripheral clock
- Dedicated power supply for high current output drivers

### **LCD Controller**

- LCD controller with up to 4COM ×36SEG
- Internal or external voltage generation
- Duty cycle: Selectable from options: 1/2, 1/3 and 1/4
- Fixed 1/3 bias
- Programmable frame period
- Clock source selectable from four options (main clock, peripheral clock, subclock or RC oscillator clock)
- Internal divider resistors or external divider resistors
- On-chip data memory for display
- LCD display can be operated in Timer Mode
- Blank display: selectable
- All SEG, COM and V pins can be switched between general and specialized purposes

### **Sound Generator**

- 8-bit PWM signal is mixed with tone frequency from 16-bit reload counter
- PWM clock by internal prescaler: 1, 1/2, 1/4, 1/8 of peripheral clock

#### **Real Time Clock**

- Operational on main oscillation (4MHz), sub oscillation (32kHz) or RC oscillation (100kHz/2MHz)
- Capable to correct oscillation deviation of Sub clock or RC oscillator clock (clock calibration)
- Read/write accessible second/minute/hour registers



- Can signal interrupts every half second/second/minute/hour/day
- Internal clock divider and prescaler provide exact 1s clock

#### **External Interrupts**

- Edge or Level sensitive
- Interrupt mask bit per channel
- Each available CAN channel RX has an external interrupt for wake-up
- Selected USART channels SIN have an external interrupt for wake-up

### Non Maskable Interrupt

- Disabled after reset, can be enabled by Boot-ROM depending on ROM configuration block
- Once enabled, cannot be disabled other than by reset
- High or Low level sensitive
- Pin shared with external interrupt 0

#### I/O Ports

- Most of the external pins can be used as general purpose I/O
- All push-pull outputs(except when used as I<sup>2</sup>C SDA/SCL line)
- Bit-wise programmable as input/output or peripheral signal
- Bit-wise programmable input enable
- One input level per GPIO-pin (either Automotive or CMOS hysteresis)
- Bit-wise programmable pull-up resistor

## **Built-in On Chip Debugger (OCD)**

- One-wire debug tool interface
- Break function:
  - ☐ Hardware break: 6 points (shared with code event)
  - □ Software break: 4096 points
- Event function
  - □ Code event: 6 points (shared with hardware break)
- □ Data event: 6 points
- □ Event sequencer: 2 levels + reset
- Execution time measurement function
- Trace function: 42 branches
- Security function

#### Flash Memory

- Dual operation flash allowing reading of one Flash bank while programming or erasing the other bank
- Command sequencer for automatic execution of programming algorithm and for supporting DMA for programming of the Flash Memory
- Supports automatic programming, Embedded Algorithm
- Write/Erase/Erase-Suspend/Resume commands
- A flag indicating completion of the automatic algorithm
- Erase can be performed on each sector individually
- Sector protection
- Flash Security feature to protect the content of the Flash
- Low voltage detection during Flash erase or write



## **Contents**

1.	Product Lineup5
2.	Block Diagram6
3.	Pin Assignment7
4.	Pin Description8
5.	Pin Circuit Type10
6.	I/O Circuit Type13
7.	Memory Map20
8.	RAM Start Addresses21
9.	User ROM Memory Map for Flash Devices22
10.	<b>Serial Programming Communication Interface 23</b>
11.	Interrupt Vector Table24
12.	Harrier Branch (free page 1)
12.	Handling Precautions28
12. 12.1	Precautions for Product Design
12.1	Precautions for Product Design28
12.1 12.2	Precautions for Product Design
12.1 12.2 12.3	Precautions for Product Design
12.1 12.2 12.3 <b>13.</b>	Precautions for Product Design
12.1 12.2 12.3 <b>13.</b> 13.1	Precautions for Product Design
12.1 12.2 12.3 <b>13.</b> 13.1 13.2	Precautions for Product Design
12.1 12.2 12.3 <b>13.</b> 13.1 13.2 13.3	Precautions for Product Design

13.7	Turn on Sequence of Power Supply to A/D Converte	er
	and Analog Inputs	34
13.8	Pin Handling when not using the A/D Converter	34
13.9	Notes on Power-on	34
13.10	Stabilization of Power Supply Voltage	34
13.11	I SMC Power Supply Pins	34
13.12	2 Serial Communication	34
13.13	B Mode Pin (MD)	34
14.	Electrical Characteristics	35
14.1	Absolute Maximum Ratings	35
14.2	Recommended Operating Conditions	37
14.3	DC Characteristics	38
14.4	AC Characteristics	44
14.5	A/D Converter	53
14.6	High Current Output Slew Rate	57
14.7	Low Voltage Detection Function Characteristics	57
14.8	Flash Memory Write/Erase Characteristics	59
15.	Example Characteristics	60
16.	Ordering Information	63
17.	Package Dimension	64
18.	Major Changes	65
Docu	ument History	72
	s, Solutions, and Legal Information	



# 1. Product Lineup


Featu	ures	CY96690	Remark
Product Type		Flash Memory Product	
Subclock		Subclock can be set by software	
Dual Operation Flash Memo	ory RAM	-	
64.5KB + 32KB	8KB	CY96F693R, CY96F693A	Product Options
128.5KB + 32KB	8KB	CY96F695R, CY96F695A	R: MCU with CAN
256.5KB + 32KB	16KB	CY96F696R	A: MCU without CAN
	1	LQFP-100	
Package		LQI100	
DMA		4ch	
USART		5ch	LIN-USART 0 to 2/4/5
with automatic	c LIN-Header		
transmission/i	reception		1 IN 1 1 2 A D.T. 0/4
with 16 byte F	RX- and	2ch	LIN-USART 0/1
TX-FIFO			
I <sup>2</sup> C		1ch	I <sup>2</sup> C 0
		27ah	AN 2 to 4/6 to 8/10 to 12/
8/10-bit A/D Converter		27ch	14 to 31
with Data Buff	fer	No	
with Range C	omparator	Yes	
with Scan Dis		Yes	
with ADC Puls	se Detection	Yes	
16-bit Reload Timer (RLT)		5ch	RLT 0 to 3/6
16-bit Free-Running Timer (	FRT)	2ch	FRT 0/1
,	,		ICU 0/1/4 to 7
16-bit Input Capture Unit (IC	:U)	6ch	(ICU 0/1/4 to 6
	•	(5 channels for LIN-USART)	for LIN-USART)
16-bit Output Compare Unit	(OCU)	4ch	OCU 0 to 3
8/16-bit Programmable Puls	e Generator (PPG)	10ch (16-bit) / 14ch (8-bit)	PPG 0 to 7/14/15
with Timing po	oint capture	Yes	
with Start dela		Yes	
with Ramp	•	No	
CANIJataria		4.56	CAN 0
CAN Interface		1ch	32 Message Buffers
Stepping Motor Controller (S	SMC)	4ch	SMC 0 to 2/4
External Interrupts (INT)		16ch	INT 0 to 15
Non-Maskable Interrupt (NM	11)	1ch	
Sound Generator (SG)	•	2ch	SG 0/1
``			COM 0 to 3
LCD Controller		4COM × 36SEG	SEG 0 to 4/7/
			11 to 28/30/33/36 to 45
Real Time Clock (RTC)		1ch	
I/O Ports		75 (Dual clock mode)	
I/O FUILS		77 (Single clock mode)	
Clock Calibration Unit (CAL)		1ch	
Clock Output Function		2ch	
Low Voltage Detection Fund	etion	Yes	Low voltage detection function can be
			disabled by software
Hardware Watchdon Timer		Yes	
nardware watchdog rimer			
Hardware Watchdog Timer On-chip RC-oscillator		Yes	

### Note:

All signals of the peripheral function in each product cannot be allocated by limiting the pins of package.
 It is necessary to use the port relocate function of the general I/O port according to your function use.




## 2. Block Diagram





## 3. Pin Assignment





# 4. Pin Description

Pin Name	Feature	Description
ADTG	ADC	A/D converter trigger input pin
ANn	ADC	A/D converter channel n input pin
AVcc	Supply	Analog circuits power supply pin
AVRH	ADC	A/D converter high reference voltage input pin
AVRL	ADC	A/D converter low reference voltage input pin
AVss	Supply	Analog circuits power supply pin
С	Voltage regulator	Internally regulated power supply stabilization capacitor pin
CKOTn	Clock Output function	Clock Output function n output pin
CKOTn_R	Clock Output function	Relocated Clock Output function n output pin
CKOTXn	Clock Output function	Clock Output function n inverted output pin
CKOTXn_R	Clock Output function	Relocated Clock Output function n inverted output pin
COMn	LCD	LCD Common driver pin
DEBUG I/F	OCD	On Chip Debugger input/output pin
DVcc	Supply	SMC pins power supply
DVss	Supply	SMC pins power supply
FRCKn	Free-Running Timer	Free-Running Timer n input pin
FRCKn_R	Free-Running Timer	Relocated Free-Running Timer n input pin
INn	ICU	Input Capture Unit n input pin
INn_R	ICU	Relocated Input Capture Unit n input pin
INTn	External Interrupt	External Interrupt n input pin
INTn_R	External Interrupt	Relocated External Interrupt n input pin
MD	Core	Input pin for specifying the operating mode
NMI	External Interrupt	Non-Maskable Interrupt input pin
OUTn	OCU	Output Compare Unit n waveform output pin
OUTn_R	OCU	Relocated Output Compare Unit n waveform output pin
Pnn_m	GPIO	General purpose I/O pin
PPGn	PPG	Programmable Pulse Generator n output pin (16bit/8bit)
PPGn_R	PPG	Relocated Programmable Pulse Generator n output pin (16bit/8bit)
PPGn_B	PPG	Programmable Pulse Generator n output pin (16bit/8bit)
PWMn	SMC	SMC PWM high current output pin
RSTX	Core	Reset input pin
RXn	CAN	CAN interface n RX input pin
SCKn	USART	USART n serial clock input/output pin
SCKn_R	USART	Relocated USART n serial clock input/output pin
SCLn	I <sup>2</sup> C	I <sup>2</sup> C interface n clock I/O input/output pin
SDAn	I <sup>2</sup> C	I <sup>2</sup> C interface n serial data I/O input/output pin
SEGn	LCD	LCD Segment driver pin
SGAn	Sound Generator	Sound Generator amplitude output pin
SGAn_R	Sound Generator	Relocated Sound Generator amplitude output pin
SGOn	Sound Generator	Sound Generator sound/tone output pin
SGOn_R	Sound Generator	Relocated Sound Generator sound/tone output pin



Pin Name	Feature	Description
SINn	USART	USART n serial data input pin
SINn_R	USART	Relocated USART n serial data input pin
SOTn	USART	USART n serial data output pin
SOTn_R	USART	Relocated USART n serial data output pin
TINn	Reload Timer	Reload Timer n event input pin
TOTn	Reload Timer	Reload Timer n output pin
TTGn	PPG	Programmable Pulse Generator n trigger input pin
TXn	CAN	CAN interface n TX output pin
Vn	LCD	LCD voltage reference pin
Vcc	Supply	Power supply pin
Vss	Supply	Power supply pin
WOT	RTC	Real Time clock output pin
WOT_R	RTC	Relocated Real Time clock output pin
X0	Clock	Oscillator input pin
X0A	Clock	Subclock Oscillator input pin
X1	Clock	Oscillator output pin
X1A	Clock	Subclock Oscillator output pin



5. Pin Circuit Type

Pin No.	I/O Circuit Type*	Pin Name
1	Supply	Vss
2	F	С
3	Р	P03_7 / INT1 / SIN1 / SEG40
4	J	P13_0 / INT2 / SOT1 / SEG41
5	Р	P13_1 / INT3 / SCK1 / SEG42
6	J	P13_2 / PPG0 / TIN0 / FRCK1 / SEG43
7	J	P13_3 / PPG1 / TOT0 / WOT / SEG44
8	Р	P13_4 / SIN0 / INT6 / SEG45
9	н	P13_5 / SOT0 / ADTG / INT7
10	М	P13_6 / SCK0 / CKOTX0
11	N	P04_4 / PPG3 / SDA0
12	N	P04_5 / PPG4 / SCL0
13	ı	P06_2 / AN2 / INT5 / SIN5
14	К	P06_3 / AN3 / FRCK0
15	К	P06_4 / AN4 / IN0 / TTG0 / TTG4
16	К	P06_6 / AN6 / TIN1 / IN4_R
17	К	P06_7 / AN7 / TOT1 / IN5_R
18	Supply	AVcc
19	G	AVRH
20	G	AVRL
21	Supply	AVss
22	К	P05_0 / AN8
23	К	P05_2 / AN10 / OUT2 / SGO1
24	К	P05_3 / AN11 / OUT3 / SGA1
25	Supply	Vcc
26	Supply	Vss
27	К	P05_4 / AN12 / INT2_R / WOT_R
28	К	P05_6 / AN14 / TIN2 / SGO1_R
29	К	P05_7 / AN15 / TOT2 / SGA1_R
30	R	P08_0 / PWM1P0 / AN16
31	R	P08_1 / PWM1M0 / AN17
32	R	P08_2 / PWM2P0 / AN18
33	R	P08_3 / PWM2M0 / AN19
34	R	P08_4 / PWM1P1 / AN20
35	Supply	DVcc
36	Supply	DVss
37	R	P08_5 / PWM1M1 / AN21
38	R	P08_6 / PWM2P1 / AN22 / PPG6_B



Pin No.	I/O Circuit Type*	Pin Name
39	R	P08_7 / PWM2M1 / AN23 / PPG7_B
40	R	P09_0 / PWM1P2 / AN24
41	R	P09_1 / PWM1M2 / AN25
42	R	P09_2 / PWM2P2 / AN26
43	R	P09_3 / PWM2M2 / AN27
44	Supply	$DV_{cc}$
45	Supply	$DV_{ss}$
46	S	P10_0 / PWM1P4 / SIN2 / TIN3 / INT11 / AN28
47	R	P10_1 / PWM1M4 / SOT2 / TOT3 / AN29
48	S	P10_2 / PWM2P4 / SCK2 / PPG6 / AN30
49	R	P10_3 / PWM2M4 / PPG7 / AN31
50	Supply	Vcc
51	Supply	$V_{ss}$
52	0	DEBUG I/F
53	Н	P17_0
54	С	MD
55	А	X0
56	А	X1
57	Supply	$V_{ss}$
58	В	P04_0 / X0A
59	В	P04_1 / X1A
60	С	RSTX
61	J	P11_0 / COM0
62	J	P11_1 / COM1 / PPG0_R
63	J	P11_2 / COM2 / PPG1_R
64	J	P11_3 / COM3 / PPG2_R
65	J	P11_4 / SEG0 / PPG3_R
66	J	P11_5 / SEG1 / PPG4_R
67	J	P11_6 / SEG2 / FRCK0_R
68	J	P11_7 / SEG3 / IN0_R
69	J	P12_0 / SEG4 / IN1_R
70	J	P12_3 / SEG7 / OUT2_R
71	J	P12_7 / SEG11 / INT1_R
72	J	P00_0 / SEG12 / INT3_R
73	J	P00_1 / SEG13 / INT4_R
74	J	P00_2 / SEG14 / INT5_R
75	Supply	V <sub>cc</sub>
76	Supply	$V_{ss}$
77	J	P00_3 / SEG15 / INT6_R




Pin No.	I/O Circuit Type*	Pin Name
78	J	P00_4 / SEG16 / INT7_R
79	J	P00_5 / SEG17 / IN6 / TTG2 / TTG6
80	J	P00_6 / SEG18 / IN7 / TTG3 / TTG7
81	J	P00_7 / SEG19 / SGO0 / INT14
82	J	P01_0 / SEG20 / SGA0
83	J	P01_1 / SEG21 / CKOT1 / OUT0
84	J	P01_2 / SEG22 / CKOTX1 / OUT1 / INT15
85	J	P01_3 / SEG23 / PPG5
86	Р	P01_4 / SEG24 / SIN4 / INT8
87	J	P01_5 / SEG25 / SOT4
88	Р	P01_6 / SEG26 / SCK4 / TTG12
89	J	P01_7 / SEG27 / CKOTX1_R / INT9 / TTG13
90	J	P02_0 / SEG28 / CKOT1_R / INT10 / TTG14
91	J	P02_2 / SEG30 / IN7_R / CKOT0_R / INT12
92	Р	P02_5 / SEG33 / OUT0_R / INT13 / SIN5_R
93	L	P03_0 / V0 / SEG36 / PPG4_B
94	L	P03_1 / V1 / SEG37 / PPG5_B
95	L	P03_2 / V2 / SEG38 / PPG14_B / SOT5_R
96	Q	P03_3 / V3 / SEG39 / PPG15_B / SCK5_R
97	M	P03_4 / RX0 / INT4
98	Н	P03_5 / TX0
99	Н	P03_6 / INT0 / NMI
100	Supply	V <sub>cc</sub>


<sup>\*:</sup> See I/O Circuit Type" for details on the I/O circuit types.



# 6. I/O Circuit Type









Туре	Circuit	Remarks
С	R Hysteresis inputs	CMOS hysteresis input pin
F	P-ch N-ch	Power supply input protection circuit
G	P-ch N-ch	<ul> <li>A/D converter ref+ (AVRH)/ ref-(AVRL) power supply input pin with protection circuit</li> <li>Without protection circuit against V<sub>cc</sub> for pins AVRH/AVRL</li> </ul>
Н	Pull-up control P-ch P-ch Nout N-ch Nout Automotive input for input shutdown	<ul> <li>■ CMOS level output (I<sub>OL</sub> = 4mA, I<sub>OH</sub> = -4mA)</li> <li>■ Automotive input with input shutdown function</li> <li>■ Programmable pull-up resistor</li> </ul>



Туре	Circuit	Remarks
I	Pull-up control	■ CMOS level output (I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA) ■ CMOS hysteresis input with input shutdown function
	P-ch P-ch Pout	Programmable pull-up resistor     Analog input
	N-ch Nout	
	Standby control Hysteresis input for input shutdown	
	Analog input	
J	Pull-up control	■ CMOS level output (I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA) ■ Automotive input with input
	P-ch P-ch Pout	shutdown function  Programmable pull-up resistor  SEG or COM output
	N-ch Nout	
	Standby control for input shutdown	
	SEG or COM output	
К	Pull-up control	■ CMOS level output  (I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA) ■ Automotive input with input
	P-ch P-ch Pout	shutdown function  Programmable pull-up resistor  Analog input
	N-ch Nout	
	Standby control for input shutdown	
	Analog input	



Туре	Circuit	Remarks
L	Pull-up control	■ CMOS level output (I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA)
	P-ch P-ch Pout	<ul> <li>Automotive input with input shutdown function</li> <li>Programmable pull-up resistor</li> <li>Vn input or SEG output</li> </ul>
	N-ch Nout	- Virinput of SEG output
	Standby control for input shutdown	
	Vn input or SEG output	
М	Pull-up control	■ CMOS level output (I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA) ■ CMOS hysteresis input with input shutdown function
	P-ch P-ch Pout	■ Programmable pull-up resistor
	N-ch Nout	
	Standby control Hysteresis input for input shutdown	
N		■ CMOS level output (I <sub>OL</sub> = 3mA, I <sub>OH</sub> = -3mA)
	Pull-up control	<ul><li>CMOS hysteresis input with input shutdown function</li><li>Programmable pull-up resistor</li></ul>
	P-ch P-ch Pout	*: N-channel transistor has slew rate control according to I <sup>2</sup> C spec, irrespective of usage.
	N-ch Nout*	
	Standby control Hysteresis input for input shutdown	



Туре	Circuit	Remarks
0	Standby control TTL input	<ul> <li>■ Open-drain I/O</li> <li>■ Output 25mA, Vcc = 2.7V</li> <li>■ TTL input</li> </ul>
P	Pull-up control  Pout  Nout  Nout  Hysteresis input  Standby control for input shutdown  SEG or COM output	<ul> <li>■ CMOS level output (I<sub>OL</sub> = 4mA, I<sub>OH</sub> = -4mA)</li> <li>■ CMOS hysteresis inputs with input shutdown function</li> <li>■ Programmable pull-up resistor</li> <li>■ SEG or COM output</li> </ul>
Q	Pull-up control P-ch Pout Nout Nout Hysteresis input for input shutdown  Vn input or SEG output	<ul> <li>■ CMOS level output         (I<sub>OL</sub> = 4mA, I<sub>OH</sub> = -4mA)</li> <li>■ CMOS hysteresis inputs with input shutdown function</li> <li>■ Programmable pull-up resistor</li> <li>■ Vn input or SEG output</li> </ul>



Туре	Circuit	Remarks
R	Pull-up control	■ CMOS level output (programmable I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA and I <sub>OL</sub> = 30mA, I <sub>OH</sub> = -30mA)
	P-ch P-ch Pout	<ul> <li>Automotive input with input shutdown function</li> </ul>
	N-ch N-ch Nout	<ul><li>Programmable pull-up / pull-down resistor</li><li>Analog input</li></ul>
	Pull-down control	
	Standby control for input shutdown	
	Analog input	
S	Pull-up control	■ CMOS level output (programmable I <sub>OL</sub> = 4mA, I <sub>OH</sub> = -4mA and I <sub>OL</sub> = 30mA, I <sub>OH</sub> = -30mA)
	P-ch P-ch Pout	■ CMOS hysteresis input with input shutdown function
		Programmable pull-up / pull-down resistor
	N-ch N-ch Nout	■ Analog input
	Pull-down control	
	Standby control Hysteresis input for input shutdown	
	Analog input	



# 7. Memory Map

FF:FFFF <sub>H</sub>	
	USER ROM*1
DE:0000 <sub>H</sub>	
DD:FFFF <sub>H</sub>	
	Reserved
	110001100
10:0000 <sub>H</sub>	
0F:C000 <sub>H</sub>	Boot-ROM
05,0000	Peripheral
0E:9000 <sub>H</sub>	
	Reserved
	reserved
01:0000 <sub>Н</sub>	
01.0000H	ROM/RAM
00:8000 <sub>H</sub>	MIRROR
	Internal RAM
RAMSTART0*2	bank0
	Reserved
00:0С00 <sub>Н</sub>	
00:0380 <sub>Н</sub>	Peripheral
00:0180 <sub>H</sub>	GPR*3
00:0100 <sub>H</sub>	DMA
00:00F0 <sub>H</sub>	Reserved
00:000 <sub>H</sub>	Peripheral

<sup>\*1:</sup> For details about USER ROM area, see "User ROM Memory Map for Flash Devices" on the following pages.

GPR: General-Purpose Register

The DMA area is only available if the device contains the corresponding resource.

The available RAM and ROM area depends on the device.

<sup>\*2:</sup> For RAMSTART addresses, see the table on the next page.

<sup>\*3:</sup> Unused GPR banks can be used as RAM area.



## 8. RAM Start Addresses

Devices	Bank 0 RAM Size	RAMSTART0
CY96F693 CY96F695	8KB	00:6200 <sub>H</sub>
CY96F696	16KB	00:4200 <sub>H</sub>



# 9. User ROM Memory Map for Flash Devices

		CY96F693	CY96F695	CY96F696	
CPU mode address	Flash memory mode address	Flash size 64.5KB + 32KB	Flash size 128.5KB + 32KB	Flash size 256.5KB + 32KB	
FF:FFFF <sub>H</sub> FF:0000 <sub>H</sub>	3F:FFFF <sub>H</sub> 3F:0000 <sub>H</sub>	SA39 - 64KB	SA39 - 64KB	SA39 - 64KB	
FE:FFFF <sub>H</sub> FE:0000 <sub>H</sub>	3E:FFFF <sub>H</sub> 3E:0000 <sub>H</sub>		SA38 - 64KB	SA38 - 64KB	Bank A of Flash
FD:FFFF <sub>H</sub> FD:0000 <sub>H</sub>	3D:FFFF <sub>н</sub> 3D:0000 <sub>н</sub>			SA37 - 64KB	Dank A of Flash
FC:FFFF <sub>H</sub> FC:0000 <sub>H</sub> FB:FFFF <sub>H</sub>	3С:FFFF <sub>н</sub> 3С:0000 <sub>н</sub>			SA36 - 64KB	
DF:A000 <sub>H</sub>	1F:9FFF <sub>H</sub>	Reserved	Reserved	Reserved	
DF:8000 <sub>H</sub>	1F:8000 <sub>H</sub>	SA4 - 8KB	SA4 - 8KB	SA4 - 8KB	
DF:7FFF <sub>H</sub> DF:6000 <sub>H</sub>	1F:7FFF <sub>H</sub> 1F:6000 <sub>H</sub>	SA3 - 8KB	SA3 - 8KB	SA3 - 8KB	Bank B of Flash
DF:5FFF <sub>H</sub> DF:4000 <sub>H</sub>	1F:5FFF <sub>H</sub> 1F:4000 <sub>H</sub>	SA2 - 8KB	SA2 - 8KB	SA2 - 8KB	
DF:3FFF <sub>H</sub> DF:2000 <sub>H</sub>	1F:3FFF <sub>н</sub> 1F:2000 <sub>н</sub>	SA1 - 8KB	SA1 - 8KB	SA1 - 8KB	
DF:1FFF <sub>H</sub> DF:0000 <sub>H</sub>	1F:1FFF <sub>н</sub> 1F:0000 <sub>н</sub>	SAS - 512B*	SAS - 512B*	SAS - 512B*	Bank A of Flash
DE:FFFF <sub>H</sub> DE:0000 <sub>H</sub>		Reserved	Reserved	Reserved	

<sup>\*:</sup> Physical address area of SAS-512B is from DF:0000<sub>H</sub> to DF:01FF<sub>H</sub>.

Others (from DF:0200<sub>H</sub> to DF:1FFF<sub>H</sub>) is mirror area of SAS-512B.

Sector SAS contains the ROM configuration block RCBA at CPU address DF:0000<sub>H</sub> -DF:01FF<sub>H</sub>.

SAS cannot be used for E<sup>2</sup>PROM emulation.



# 10. Serial Programming Communication Interface

USART pins for Flash serial programming (MD = 0, DEBUG I/F = 0, Serial Communication mode)

CY96690						
Pin Number	USART Number	Normal Function				
8		SIN0				
9	USART0	SOT0				
10		SCK0				
3		SIN1				
4	USART1	SOT1				
5		SCK1				
46		SIN2				
47	USART2	SOT2				
48		SCK2				
86		SIN4				
87	USART4	SOT4				
88		SCK4				



# 11. Interrupt Vector Table

Vector Number	Offset in Vector Table	Vector Name	Cleared by DMA	Index in ICR to Program	Description
0	3FC <sub>H</sub>	CALLV0	No	-	CALLV instruction
1	3F8 <sub>H</sub>	CALLV1	No	-	CALLV instruction
2	3F4 <sub>H</sub>	CALLV2	No	-	CALLV instruction
3	3F0 <sub>H</sub>	CALLV3	No	-	CALLV instruction
4	3EC <sub>H</sub>	CALLV4	No	-	CALLV instruction
5	3E8 <sub>H</sub>	CALLV5	No	-	CALLV instruction
6	3E4 <sub>H</sub>	CALLV6	No	-	CALLV instruction
7	3E0 <sub>H</sub>	CALLV7	No	-	CALLV instruction
8	3DC <sub>H</sub>	RESET	No	-	Reset vector
9	3D8 <sub>H</sub>	INT9	No	-	INT9 instruction
10	3D4 <sub>H</sub>	EXCEPTION	No	-	Undefined instruction execution
11	3D0 <sub>H</sub>	NMI	No	-	Non-Maskable Interrupt
12	3CC <sub>H</sub>	DLY	No	12	Delayed Interrupt
13	3C8 <sub>H</sub>	RC_TIMER	No	13	RC Clock Timer
14	3C4 <sub>H</sub>	MC_TIMER	No	14	Main Clock Timer
15	3C0 <sub>H</sub>	SC_TIMER	No	15	Sub Clock Timer
16	3ВСн	LVDI	No	16	Low Voltage Detector
17	3B8 <sub>H</sub>	EXTINT0	Yes	17	External Interrupt 0
18	3B4 <sub>H</sub>	EXTINT1	Yes	18	External Interrupt 1
19	3B0 <sub>H</sub>	EXTINT2	Yes	19	External Interrupt 2
20	3AC <sub>H</sub>	EXTINT3	Yes	20	External Interrupt 3
21	3A8 <sub>H</sub>	EXTINT4	Yes	21	External Interrupt 4
22	3A4 <sub>H</sub>	EXTINT5	Yes	22	External Interrupt 5
23	3A0 <sub>H</sub>	EXTINT6	Yes	23	External Interrupt 6
24	39C <sub>H</sub>	EXTINT7	Yes	24	External Interrupt 7
25	398 <sub>H</sub>	EXTINT8	Yes	25	External Interrupt 8
26	394 <sub>H</sub>	EXTINT9	Yes	26	External Interrupt 9
27	390 <sub>H</sub>	EXTINT10	Yes	27	External Interrupt 10
28	38C <sub>H</sub>	EXTINT11	Yes	28	External Interrupt 11
29	388 <sub>H</sub>	EXTINT12	Yes	29	External Interrupt 12
30	384 <sub>H</sub>	EXTINT13	Yes	30	External Interrupt 13
31	380 <sub>H</sub>	EXTINT14	Yes	31	External Interrupt 14
32	37C <sub>H</sub>	EXTINT15	Yes	32	External Interrupt 15
33	378 <sub>H</sub>	CAN0	No	33	CAN Controller 0
34	374 <sub>H</sub>	-	-	34	Reserved
35	370 <sub>H</sub>	-	-	35	Reserved
36	36C <sub>H</sub>	-	-	36	Reserved
37	368 <sub>H</sub>	-	-	37	Reserved
38	364 <sub>H</sub>	PPG0	Yes	38	Programmable Pulse Generator 0
39	360 <sub>H</sub>	PPG1	Yes	39	Programmable Pulse Generator 1



Vector Number	Offset in Vector Table	Vector Name	Cleared by DMA	Index in ICR to Program	Description
40	35C <sub>H</sub>	PPG2	Yes	40	Programmable Pulse Generator 2
41	358 <sub>H</sub>	PPG3	Yes	41	Programmable Pulse Generator 3
42	354 <sub>H</sub>	PPG4	Yes	42	Programmable Pulse Generator 4
43	350 <sub>H</sub>	PPG5	Yes	43	Programmable Pulse Generator 5
44	34C <sub>H</sub>	PPG6	Yes	44	Programmable Pulse Generator 6
45	348 <sub>H</sub>	PPG7	Yes	45	Programmable Pulse Generator 7
46	344 <sub>H</sub>	-	-	46	Reserved
47	340 <sub>H</sub>	-	-	47	Reserved
48	33C <sub>H</sub>	-	-	48	Reserved
49	338 <sub>H</sub>	-	-	49	Reserved
50	334 <sub>H</sub>	-	-	50	Reserved
51	330 <sub>H</sub>	-	-	51	Reserved
52	32C <sub>H</sub>	PPG14	Yes	52	Programmable Pulse Generator 14
53	328 <sub>H</sub>	PPG15	Yes	53	Programmable Pulse Generator 15
54	324 <sub>H</sub>	-	-	54	Reserved
55	320 <sub>H</sub>	-	-	55	Reserved
56	31C <sub>H</sub>	-	-	56	Reserved
57	318 <sub>H</sub>	-	-	57	Reserved
58	314 <sub>H</sub>	RLT0	Yes	58	Reload Timer 0
59	310 <sub>H</sub>	RLT1	Yes	59	Reload Timer 1
60	30C <sub>H</sub>	RLT2	Yes	60	Reload Timer 2
61	308 <sub>H</sub>	RLT3	Yes	61	Reload Timer 3
62	304н	-	-	62	Reserved
63	300 <sub>H</sub>	-	-	63	Reserved
64	2FC <sub>H</sub>	RLT6	Yes	64	Reload Timer 6
65	2F8 <sub>H</sub>	ICU0	Yes	65	Input Capture Unit 0
66	2F4 <sub>H</sub>	ICU1	Yes	66	Input Capture Unit 1
67	2F0 <sub>H</sub>	-	-	67	Reserved
68	2EC <sub>H</sub>	-	-	68	Reserved
69	2E8 <sub>H</sub>	ICU4	Yes	69	Input Capture Unit 4
70	2E4 <sub>H</sub>	ICU5	Yes	70	Input Capture Unit 5
71	2E0 <sub>H</sub>	ICU6	Yes	71	Input Capture Unit 6
72	2DC <sub>H</sub>	ICU7	Yes	72	Input Capture Unit 7
73	2D8 <sub>H</sub>	-	=	73	Reserved
74	2D4 <sub>H</sub>	-	=	74	Reserved
75	2D0 <sub>H</sub>	-	-	75	Reserved
76	2CC <sub>H</sub>	-	-	76	Reserved
77	2C8 <sub>H</sub>	OCU0	Yes	77	Output Compare Unit 0
78	2C4 <sub>H</sub>	OCU1	Yes	78	Output Compare Unit 1
79	2C0 <sub>H</sub>	OCU2	Yes	79	Output Compare Unit 2
80	2BC <sub>H</sub>	OCU3	Yes	80	Output Compare Unit 3
81	2B8 <sub>H</sub>	-	-	81	Reserved



Vector Number	Offset in Vector Table	Vector Name	Cleared by DMA	Index in ICR to Program	Description
82	2B4 <sub>H</sub>	-	-	82	Reserved
83	2B0 <sub>H</sub>	-	-	83	Reserved
84	2AC <sub>H</sub>	-	-	84	Reserved
85	2A8 <sub>H</sub>	-	-	85	Reserved
86	2A4 <sub>H</sub>	-	-	86	Reserved
87	2A0 <sub>H</sub>	-	-	87	Reserved
88	29C <sub>H</sub>	-	-	88	Reserved
89	298н	FRT0	Yes	89	Free-Running Timer 0
90	294 <sub>H</sub>	FRT1	Yes	90	Free-Running Timer 1
91	290 <sub>H</sub>	-	-	91	Reserved
92	28C <sub>H</sub>	-	-	92	Reserved
93	288 <sub>H</sub>	RTC0	No	93	Real Time Clock
94	284 <sub>H</sub>	CAL0	No	94	Clock Calibration Unit
95	280 <sub>H</sub>	SG0	No	95	Sound Generator 0
96	27C <sub>H</sub>	IIC0	Yes	96	I <sup>2</sup> C interface 0
97	278 <sub>H</sub>	-	-	97	Reserved
98	274 <sub>H</sub>	ADC0	Yes	98	A/D Converter 0
99	270 <sub>H</sub>	-	-	99	Reserved
100	26C <sub>H</sub>	-	-	100	Reserved
101	268 <sub>H</sub>	LINR0	Yes	101	LIN USART 0 RX
102	264 <sub>H</sub>	LINT0	Yes	102	LIN USART 0 TX
103	260 <sub>H</sub>	LINR1	Yes	103	LIN USART 1 RX
104	25C <sub>H</sub>	LINT1	Yes	104	LIN USART 1 TX
105	258 <sub>H</sub>	LINR2	Yes	105	LIN USART 2 RX
106	254 <sub>H</sub>	LINT2	Yes	106	LIN USART 2 TX
107	250 <sub>H</sub>	-	-	107	Reserved
108	24C <sub>H</sub>	-	-	108	Reserved
109	248 <sub>H</sub>	LINR4	Yes	109	LIN USART 4 RX
110	244 <sub>H</sub>	LINT4	Yes	110	LIN USART 4 TX
111	240 <sub>H</sub>	LINR5	Yes	111	LIN USART 5 RX
112	23C <sub>H</sub>	LINT5	Yes	112	LIN USART 5 TX
113	238 <sub>H</sub>	-	-	113	Reserved
114	234 <sub>H</sub>	-	-	114	Reserved
115	230 <sub>H</sub>	-	-	115	Reserved
116	22C <sub>H</sub>	-	-	116	Reserved
117	228 <sub>H</sub>	-	-	117	Reserved
118	224 <sub>H</sub>	-	-	118	Reserved
119	220 <sub>H</sub>	-	-	119 Reserved	
120	21C <sub>H</sub>	-	-	120	Reserved
121	218 <sub>H</sub>	SG1	No	121	Sound Generator 1
122	214 <sub>H</sub>	-	-	122	Reserved
123	210 <sub>H</sub>	-	-	123	Reserved



Vector Number	Offset in Vector Table	Vector Name	Cleared by DMA	Index in ICR to Program	Description	
124	20C <sub>H</sub>	-	-	124	Reserved	
125	208 <sub>H</sub>	-	-	125	Reserved	
126	204 <sub>H</sub>	-	-	126	Reserved	
127	200 <sub>H</sub>	-	-	127	Reserved	
128	1FC <sub>H</sub>	-	-	128	Reserved	
129	1F8 <sub>H</sub>	-	-	129	Reserved	
130	1F4 <sub>H</sub>	-	-	130	Reserved	
131	1F0 <sub>H</sub>	-	-	131	Reserved	
132	1EC <sub>H</sub>	-	-	132	Reserved	
133	1E8 <sub>H</sub>	FLASHA	Yes	133	Flash memory A interrupt	
134	1E4 <sub>H</sub>	-	-	134	Reserved	
135	1E0 <sub>H</sub>	-	-	135	Reserved	
136	1DC <sub>H</sub>	-	-	136	Reserved	
137	1D8 <sub>H</sub>	-	-	137	Reserved	
138	1D4 <sub>H</sub>	-	-	138	Reserved	
139	1D0 <sub>H</sub>	ADCRC0	No	139	A/D Converter 0 - Range Comparator	
140	1CC <sub>H</sub>	ADCPD0	No	140	A/D Converter 0 - Pulse detection	
141	1C8 <sub>H</sub>	-	-	141	Reserved	
142	1C4 <sub>H</sub>	-	-	142	Reserved	
143	1C0 <sub>H</sub>	-	-	143	Reserved	



## 12. Handling Precautions

Any semiconductor devices have inherently a certain rate of failure. The possibility of failure is greatly affected by the conditions in which they are used (circuit conditions, environmental conditions, etc.). This page describes precautions that must be observed to minimize the chance of failure and to obtain higher reliability from your Cypress semiconductor devices.

#### 12.1 Precautions for Product Design

This section describes precautions when designing electronic equipment using semiconductor devices.

## ■ Absolute Maximum Ratings

Semiconductor devices can be permanently damaged by application of stress (voltage, current, temperature, etc.) in excess of certain established limits, called absolute maximum ratings. Do not exceed these ratings.

#### ■ Recommended Operating Conditions

Recommended operating conditions are normal operating ranges for the semiconductor device. All the device's electrical characteristics are warranted when operated within these ranges.

Always use semiconductor devices within the recommended operating conditions. Operation outside these ranges may adversely affect reliability and could result in device failure.

No warranty is made with respect to uses, operating conditions, or combinations not represented on the data sheet. Users considering application outside the listed conditions are advised to contact their sales representative beforehand.

#### ■ Processing and Protection of Pins

These precautions must be followed when handling the pins which connect semiconductor devices to power supply and input/output functions.

## 1. Preventing Over-Voltage and Over-Current Conditions

Exposure to voltage or current levels in excess of maximum ratings at any pin is likely to cause deterioration within the device and in extreme cases leads to permanent damage of the device. Try to prevent such overvoltage or over-current conditions at the design stage.

## 2. Protection of Output Pins

Shorting of output pins to supply pins or other output pins, or connection to large capacitance can cause large current flows. Such conditions if present for extended periods of time can damage the device.

Therefore, avoid this type of connection.

### 3. Handling of Unused Input Pins

Unconnected input pins with very high impedance levels can adversely affect stability of operation. Such pins should be connected through an appropriate resistance to a power supply pin or ground pin.

#### ■ Latch-up

Semiconductor devices are constructed by the formation of P-type and N-type areas on a substrate. When subjected to abnormally high voltages, internal parasitic PNPN junctions (called thyristor structures) may be formed, causing large current levels in excess of several hundred mA to flow continuously at the power supply pin. This condition is called latch-up.

### **CAUTION:**

The occurrence of latch-up not only causes loss of reliability in the semiconductor device, but can cause injury or damage from high heat, smoke or flame. To prevent this from happening, do the following:

- 1. Be sure that voltages applied to pins do not exceed the absolute maximum ratings. This should include attention to abnormal noise, surge levels, etc.
- 2. Be sure that abnormal current flows do not occur during the power-on sequence.

#### ■ Observance of Safety Regulations and Standards

Most countries in the world have established standards and regulations regarding safety, protection from electromagnetic interference, etc. Customers are requested to observe applicable regulations and standards in the design of products.

Document Number: 002-04717 Rev. \*D Page 28 of 73



#### ■ Fail-Safe Design

Any semiconductor devices have inherently a certain rate of failure. You must protect against injury, damage or loss from such failures by incorporating safety design measures into your facility and equipment such as redundancy, fire protection, and prevention of over-current levels and other abnormal operating conditions.

### ■ Precautions Related to Usage of Devices

Cypress semiconductor devices are intended for use in standard applications (computers, office automation and other office equipment, industrial, communications, and measurement equipment, personal or household devices, etc.).

#### **CAUTION:**

Customers considering the use of our products in special applications where failure or abnormal operation may directly affect human lives or cause physical injury or property damage, or where extremely high levels of reliability are demanded (such as aerospace systems, atomic energy controls, sea floor repeaters, vehicle operating controls, medical devices for life support, etc.) are requested to consult with sales representatives before such use. The company will not be responsible for damages arising from such use without prior approval.

## 12.2 Precautions for Package Mounting

Package mounting may be either lead insertion type or surface mount type. In either case, for heat resistance during soldering, you should only mount under Cypress recommended conditions. For detailed information about mount conditions, contact your sales representative.

#### ■ Lead Insertion Type

Mounting of lead insertion type packages onto printed circuit boards may be done by two methods: direct soldering on the board, or mounting by using a socket.

Direct mounting onto boards normally involves processes for inserting leads into through-holes on the board and using the flow soldering (wave soldering) method of applying liquid solder. In this case, the soldering process usually causes leads to be subjected to thermal stress in excess of the absolute ratings for storage temperature. Mounting processes should conform to Cypress recommended mounting conditions.

If socket mounting is used, differences in surface treatment of the socket contacts and IC lead surfaces can lead to contact deterioration after long periods. For this reason it is recommended that the surface treatment of socket contacts and IC leads be verified before mounting.

### ■ Surface Mount Type

Surface mount packaging has longer and thinner leads than lead-insertion packaging, and therefore leads are more easily deformed or bent. The use of packages with higher pin counts and narrower pin pitch results in increased susceptibility to open connections caused by deformed pins, or shorting due to solder bridges.

You must use appropriate mounting techniques. Cypress recommends the solder reflow method, and has established a ranking of mounting conditions for each product. Users are advised to mount packages in accordance with Cypress ranking of recommended conditions.

## ■ Lead-Free Packaging

#### **CAUTION:**

When ball grid array (BGA) packages with Sn-Ag-Cu balls are mounted using Sn-Pb eutectic soldering, junction strength may be reduced under some conditions of use.



#### ■ Storage of Semiconductor Devices

Because plastic chip packages are formed from plastic resins, exposure to natural environmental conditions will cause absorption of moisture. During mounting, the application of heat to a package that has absorbed moisture can cause surfaces to peel, reducing moisture resistance and causing packages to crack. To prevent, do the following:

- 1. Avoid exposure to rapid temperature changes, which cause moisture to condense inside the product. Store products in locations where temperature changes are slight.
- 2. Use dry boxes for product storage. Products should be stored below 70% relative humidity, and at temperatures between 5°C and 30°C. When you open Dry Package that recommends humidity 40% to 70% relative humidity.
- 3. When necessary, Cypress packages semiconductor devices in highly moisture-resistant aluminum laminate bags, with a silica gel desiccant. Devices should be sealed in their aluminum laminate bags for storage.
- Avoid storing packages where they are exposed to corrosive gases or high levels of dust.

#### ■ Baking

Packages that have absorbed moisture may be de-moisturized by baking (heat drying). Follow the Cypress recommended conditions for baking.

Condition: 125°C/24 h

#### ■ Static Electricity

Because semiconductor devices are particularly susceptible to damage by static electricity, you must take the following precautions:

- 1. Maintain relative humidity in the working environment between 40% and 70%. Use of an apparatus for ion generation may be needed to remove electricity.
- 2. Electrically ground all conveyors, solder vessels, soldering irons and peripheral equipment.
- Eliminate static body electricity by the use of rings or bracelets connected to ground through high resistance (on the level of 1 MΩ). Wearing of conductive clothing and shoes, use of conductive floor mats and other measures to minimize shock loads is recommended.
- 4. Ground all fixtures and instruments, or protect with anti-static measures.
- 5. Avoid the use of styrofoam or other highly static-prone materials for storage of completed board assemblies.



#### 12.3 Precautions for Use Environment

Reliability of semiconductor devices depends on ambient temperature and other conditions as described above.

For reliable performance, do the following:

#### 1. Humidity

Prolonged use in high humidity can lead to leakage in devices as well as printed circuit boards. If high humidity levels are anticipated, consider anti-humidity processing.

## 2. Discharge of Static Electricity

When high-voltage charges exist close to semiconductor devices, discharges can cause abnormal operation. In such cases, use anti-static measures or processing to prevent discharges.

#### 3. Corrosive Gases, Dust, or Oil

Exposure to corrosive gases or contact with dust or oil may lead to chemical reactions that will adversely affect the device. If you use devices in such conditions, consider ways to prevent such exposure or to protect the devices.

#### 4. Radiation, Including Cosmic Radiation

Most devices are not designed for environments involving exposure to radiation or cosmic radiation. Users should provide shielding as appropriate.

#### 5. Smoke, Flame

#### CAUTION:

Plastic molded devices are flammable, and therefore should not be used near combustible substances. If devices begin to smoke or burn, there is danger of the release of toxic gases.

Customers considering the use of Cypress products in other special environmental conditions should consult with sales representatives.



## 13. Handling Devices

## Special Care is Required for the following when Handling the Device:

- Latch-up prevention
- Unused pins handling
- External clock usage
- Notes on PLL clock mode operation
- Power supply pins (Vcc/Vss)
- Crystal oscillator and ceramic resonator circuit
- Turn on sequence of power supply to A/D converter and analog inputs
- Pin handling when not using the A/D converter
- Notes on Power-on
- Stabilization of power supply voltage
- SMC power supply pins
- Serial communication
- Mode Pin (MD)

## 13.1 Latch-Up Prevention

CMOS IC chips may suffer latch-up under the following conditions:

- A voltage higher than V<sub>CC</sub> or lower than V<sub>SS</sub> is applied to an input or output pin.
- A voltage higher than the rated voltage is applied between Vcc pins and Vss pins.
- The AVcc power supply is applied before the Vcc voltage.

Latch-up may increase the power supply current dramatically, causing thermal damages to the device.

For the same reason, extra care is required to not let the analog power-supply voltage (AV<sub>CC</sub>, AVRH) exceed the digital power-supply voltage.

### 13.2 Unused Pins Handling

Unused input pins can be left open when the input is disabled (corresponding bit of Port Input Enable register PIER = 0).

Leaving unused input pins open when the input is enabled may result in misbehavior and possible permanent

damage of the device. To prevent latch-up, they must therefore be pulled up or pulled down through resistors which should be more than  $2k\Omega$ .

Unused bidirectional pins can be set either to the output state and be then left open, or to the input state with either input disabled or external pull-up/pull-down resistor as described above.

#### 13.3 External Clock Usage


The permitted frequency range of an external clock depends on the oscillator type and configuration.

See AC Characteristics for detailed modes and frequency limits. Single and opposite phase external clocks must be connected as follows:

## 13.3.1 Single Phase External Clock for Main Oscillator

When using a single phase external clock for the Main oscillator, X0 pin must be driven and X1 pin left open. And supply 1.8V power to the external clock.






#### 13.3.2 Single Phase External Clock for Sub Oscillator

When using a single phase external clock for the Sub oscillator, "External clock mode" must be selected and X0A/P04\_0 pin must be driven. X1A/P04\_1 pin can be configured as GPIO.

#### 13.3.3 Opposite Phase External Clock

When using an opposite phase external clock, X1 (X1A) pins must be supplied with a clock signal which has the opposite phase to the X0 (X0A) pins. Supply level on X0 and X1 pins must be 1.8V.



### 13.4 Notes on PLL Clock Mode Operation

If the microcontroller is operated with PLL clock mode and no external oscillator is operating or no external clock is supplied, the microcontroller attempts to work with the free oscillating PLL. Performance of this operation, however, cannot be guaranteed.

#### 13.5 Power Supply Pins (Vcc/Vss)

It is required that all  $V_{CC}$ -level as well as all  $V_{SS}$ -level power supply pins are at the same potential. If there is more than one  $V_{CC}$  or  $V_{SS}$  level, the device may operate incorrectly or be damaged even within the guaranteed operating range.

Vcc and Vss pins must be connected to the device from the power supply with lowest possible impedance.

The smoothing capacitor at Vcc pin must use the one of a capacity value that is larger than Cs.

Besides this, as a measure against power supply noise, it is required to connect a bypass capacitor of about  $0.1\mu F$  between Vcc and Vss pins as close as possible to Vcc and Vss pins.

### 13.6 Crystal Oscillator and ceramic resonator Circuit

Noise at X0, X1 pins or X0A, X1A pins might cause abnormal operation. It is required to provide bypass capacitors with shortest possible distance to X0, X1 pins and X0A, X1A pins, crystal oscillator (or ceramic resonator) and ground lines, and, to the utmost effort, that the lines of oscillation circuit do not cross the lines of other circuits.

It is highly recommended to provide a printed circuit board art work surrounding X0, X1 pins and X0A, X1A pins with a ground area for stabilizing the operation.

It is highly recommended to evaluate the quartz/MCU or resonator/MCU system at the quartz or resonator manufacturer, especially when using low-Q resonators at higher frequencies.



## 13.7 Turn on Sequence of Power Supply to A/D Converter and Analog Inputs

It is required to turn the A/D converter power supply (AVcc, AVRH, AVRL) and analog inputs (ANn) on after turning the digital power supply (Vcc) on.

It is also required to turn the digital power off after turning the A/D converter supply and analog inputs off. In this case, AVRH must not exceed AVcc . Input voltage for ports shared with analog input ports also must not exceed AVcc (turning the analog and digital power supplies simultaneously on or off is acceptable).

## 13.8 Pin Handling when not using the A/D Converter

If the A/D converter is not used, the power supply pins for A/D converter should be connected such as  $AV_{CC} = V_{CC}$ ,  $AV_{SS} = AVRH = AVRL = V_{SS}$ .

#### 13.9 Notes on Power-on

To prevent malfunction of the internal voltage regulator, supply voltage profile while turning the power supply on should be slower than 50µs from 0.2V to 2.7V.

## 13.10 Stabilization of Power Supply Voltage

If the power supply voltage varies acutely even within the operation safety range of the  $V_{CC}$  power supply voltage, a malfunction may occur. The  $V_{CC}$  power supply voltage must therefore be stabilized. As stabilization guidelines, the power supply voltage must be stabilized in such a way that  $V_{CC}$  ripple fluctuations (peak to peak value) in the commercial frequencies (50Hz to 60Hz) fall within 10% of the standard  $V_{CC}$  power supply voltage and the transient fluctuation rate becomes  $0.1V/\mu s$  or less in instantaneous fluctuation for power supply switching.

### 13.11 SMC Power Supply Pins

All DVcc /DVss pins must be set to the same level as the Vcc /Vss pins.

Note that the SMC I/O pin state is undefined if DV<sub>CC</sub> is powered on and V<sub>CC</sub> is below 3V. To avoid this, V<sub>CC</sub> must always be powered on before DV<sub>CC</sub>.

DVcc/DVss must be applied when using SMC I/O pin as GPIO.

#### 13.12 Serial Communication

There is a possibility to receive wrong data due to noise or other causes on the serial communication.

Therefore, design a printed circuit board so as to avoid noise.

Consider receiving of wrong data when designing the system. For example apply a checksum and retransmit the data if an error occurs.

## 13.13 Mode Pin (MD)

Connect the mode pin directly to Vcc or Vss pin. To prevent the device unintentionally entering test mode due to noise, lay out the printed circuit board so as to minimize the distance from the mode pin to  $V_{cc}$  or  $V_{ss}$  pin and provide a low-impedance connection.



# 14. Electrical Characteristics

## 14.1 Absolute Maximum Ratings

_	Symbol		R	ating		Remarks
Parameter		Condition	Min	Max	Unit	
Power supply voltage <sup>[1]</sup>	V <sub>CC</sub>	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	
Analog power supply voltage <sup>[1]</sup>	AV <sub>cc</sub>	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	$V_{CC} = AV_{CC}^{[2]}$
Analog reference voltage <sup>[1]</sup>	AVRH, AVRL	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	AV <sub>CC</sub> ≥ AVRH, AV <sub>CC</sub> ≥ AVRL, AVRH > AVRL, AVRL ≥ AV <sub>SS</sub>
SMC Power supply <sup>[1]</sup>	DV <sub>cc</sub>	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	$V_{CC} = AV_{CC} = DV_{CC}^{[2]}$
LCD power supply voltage <sup>[1]</sup>	V0 to V3	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	٧	V0 to V3 must not exceed V <sub>cc</sub>
Input voltage[1]	Vı	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	$V_1 \le (D)V_{CC} + 0.3V^{[3]}$
Output voltage <sup>[1]</sup>	Vo	-	V <sub>SS</sub> - 0.3	V <sub>SS</sub> + 6.0	V	$V_{\rm O} \le ({\rm D})V_{\rm CC} + 0.3V^{[3]}$
Maximum Clamp Current	I <sub>CLAMP</sub>	-	-4.0	+4.0	mA	Applicable to general purpose I/O pins [4]
Total Maximum Clamp Current	Σ I <sub>CLAMP</sub>	-	-	25	mA	Applicable to general purpose I/O pins [4]
	I <sub>OL</sub>	-	-	15	mA	Normal port
	I <sub>OLSMC</sub>	T <sub>A</sub> = -40°C	-	52	mA	High current port
"L" level maximum output current		T <sub>A</sub> = +25°C	-	39	mA	
7		T <sub>A</sub> = +85°C	-	32	mA	
		T <sub>A</sub> = +105°C	-	30	mA	
	I <sub>OLAV</sub>	-	-	4	mA	Normal port
"I " laval avanana avanut		T <sub>A</sub> = -40°C	-	40	mA	
"L" level average output current	I <sub>OLAVSMC</sub>	T <sub>A</sub> = +25°C	-	30	mA	High current port
	IOLAVSMC	T <sub>A</sub> = +85°C	-	25	mA	
		T <sub>A</sub> = +105°C	=	23	mA	
"L" level maximum	ΣI <sub>OL</sub>	-	-	50	mA	Normal port
overall output current	ΣI <sub>OLSMC</sub>	-	-	260	mA	High current port
"L" level average	ΣI <sub>OLAV</sub>	-	-	25	mA	Normal port
overall output current	ΣI <sub>OLAVSMC</sub>	-	-	170	mA	High current port
"H" level maximum	I <sub>OH</sub>	-	-	-15	mA	Normal port
output current		T <sub>A</sub> = -40°C	-	-52	mA	
	I <sub>онѕмс</sub>	T <sub>A</sub> = +25°C	-	-39	mA	High current port
	IOHSMC	T <sub>A</sub> = +85°C	-	-32	mA	I light current port
		T <sub>A</sub> = +105°C	-	-30	mA	
	I <sub>OHAV</sub>	-	-	-4	mA	Normal port
W. W. Laverdane		T <sub>A</sub> = -40°C	-	-40	mA	
"H" level average output current	I <sub>OHAVSMC</sub>	T <sub>A</sub> = +25°C	-	-30	mA	High current port
•		T <sub>A</sub> = +85°C	-	-25	mA	
		T <sub>A</sub> = +105°C	-	-23	mA	
"H" level maximum	ΣI <sub>OH</sub>	-	-	-50	mA	Normal port
overall output current	$\Sigma I_{OHSMC}$	-	-	-260	mA	High current port



Danamatan	Comple at	Condition	Ra	ting	11:4	Domonico
Parameter	Symbol	Condition	Min	Max	Unit	Remarks
"H" level average	ΣI <sub>OHAV</sub>	-	-	-25	mA	Normal port
overall output current	ΣI <sub>OHAVSMC</sub>	-	-	-170	mA	High current port
Power consumption <sup>[5]</sup>	P <sub>D</sub>	T <sub>A</sub> = +105°C	-	333 <sup>[6]</sup>	mW	
Operating ambient temperature	T <sub>A</sub>	-	-40	+105	°C	
Storage temperature	T <sub>STG</sub>	-	-55	+150	°C	

[1]: This parameter is based on  $V_{SS} = AV_{SS} = DV_{SS} = 0V$ .


[2]:  $AV_{CC}$  and  $V_{CC}$  and  $DV_{CC}$  must be set to the same voltage. It is required that  $AV_{CC}$  does not exceed  $V_{CC}$ ,  $DV_{CC}$  and that the voltage at the analog inputs does not exceed  $AV_{CC}$  when the power is switched on.

[3]:  $V_I$  and  $V_O$  should not exceed  $V_{CC} + 0.3V$ .  $V_I$  should also not exceed the specified ratings. However if the maximum current to/from an input is limited by some means with external components, the  $I_{CLAMP}$  rating supersedes the  $V_I$  rating. Input/Output voltages of high current ports depend on  $DV_{CC}$ . Input/Output voltages of standard ports depend on  $V_{CC}$ .

[4]:

- Applicable to all general purpose I/O pins (Pnn\_m).
- Use within recommended operating conditions.
- Use at DC voltage (current).
- The +B signal should always be applied a limiting resistance placed between the +B signal and the microcontroller.
- The value of the limiting resistance should be set so that when the +B signal is applied the input current to the microcontroller pin does not exceed rated values, either instantaneously or for prolonged periods.
- Note that when the microcontroller drive current is low, such as in the power saving modes, the +B input potential may pass through the protective diode and increase the potential at the V<sub>CC</sub> pin, and this may affect other devices.
- Note that if a +B signal is input when the microcontroller power supply is off (not fixed at 0V), the power supply is provided from the pins, so that incomplete operation may result.
- Note that if the +B input is applied during power-on, the power supply is provided from the pins and the resulting supply voltage may not be sufficient to operate the Power reset.
- The DEBUG I/F pin has only a protective diode against V<sub>SS</sub>. Hence it is only permitted to input a negative clamping current (4mA). For protection against positive input voltages, use an external clamping diode which limits the input voltage to maximum 6.0V.

Sample recommended circuits:



[5]: The maximum permitted power dissipation depends on the ambient temperature, the air flow velocity and the thermal conductance of the package on the PCB.

The actual power dissipation depends on the customer application and can be calculated as follows:

 $P_D = P_{IO} + P_{INT}$ 

 $P_{IO} = \Sigma (V_{OL} \times I_{OL} + V_{OH} \times I_{OH})$  (I/O load power dissipation, sum is performed on all I/O ports)

 $P_{INT} = V_{CC} \times (I_{CC} + I_A)$  (internal power dissipation)



 $I_{CC}$  is the total core current consumption into  $V_{CC}$  as described in the "DC characteristics" and depends on the selected operation mode and clock frequency and the usage of functions like Flash programming.  $I_A$  is the analog current consumption into AV $_{CC}$ .

[6]: Worst case value for a package mounted on single layer PCB at specified TA without air flow.

#### **WARNING:**

Semiconductor devices can be permanently damaged by application of stress (voltage, current, temperature, etc.) in excess of absolute maximum ratings. Do not exceed these ratings.

#### 14.2 Recommended Operating Conditions

 $(V_{SS} = AV_{SS} = DV_{SS} = 0V)$ 

	Í		Value			
Parameter	Symbol	Min Typ Max		Max	Unit	Remarks
	V <sub>CC</sub> ,	2.7	=	5.5	V	
Power supply voltage	AV <sub>CC</sub> , DV <sub>CC</sub>	2.0	-	5.5	V	Maintains RAM data in stop mode
Smoothing capacitor at C pin	Cs	0.5	1.0 to 3.9	4.7	μF	$1.0\mu F \text{ (Allowance within } \pm 50\%)$ $3.9\mu F \text{ (Allowance within } \pm 20\%)$ Please use the ceramic capacitor or the capacitor of the frequency response of this level. The smoothing capacitor at $V_{CC}$ must use the one of a capacity value that is larger than $C_S$ .

#### WARNING:

The recommended operating conditions are required in order to ensure the normal operation of the semiconductor device. All of the device's electrical characteristics are warranted when the device is operated within these ranges. Always use semiconductor devices within their recommended operating condition ranges. Operation outside these ranges may adversely affect reliability and could result in device failure. No warranty is made with respect to uses, operating conditions, or combinations not represented on the data sheet. Users considering application outside the listed conditions are advised to contact their representatives beforehand.



## 14.3 DC Characteristics

**14.3.1** *Current Rating* (Vcc = AVcc = DVcc = 2.7V to 5.5V. Vss = AVss = DVss = 0V. T<sub>A</sub> = -40°C to +105°C)

Danamartan	Constituti	Pin	Oan dittarra		Value		11	Demont
Parameter	Symbol	Name	Conditions	Min	Тур	Max	Unit	Remarks
			PLL Run mode with CLKS1/2 = CLKB = CLKP1/2 = 32MHz	-	28	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCPLL</sub>		Flash 0 wait (CLKRC and CLKSC stopped)	-	-	38	mA	T <sub>A</sub> = +105°C
			Main Run mode with CLKS1/2 = CLKB = CLKP1/2 = 4MHz	-	3.5	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCMAIN</sub>		Flash 0 wait (CLKPLL, CLKSC and CLKRC stopped)	-	-	8	mA	T <sub>A</sub> = +105°C
			RC Run mode with CLKS1/2 = CLKB = CLKP1/2 = CLKRC = 2MHz	-	1.8	-	mA	T <sub>A</sub> = +25°C
Power supply current in Run modes <sup>[1]</sup>	urrent in Run ICCRCH Vcc	Vcc	Flash 0 wait  (CLKMC, CLKPLL and CLKSC stopped)	-	-	6	mA	T <sub>A</sub> = +105°C
			RC Run mode with CLKS1/2 = CLKB = CLKP1/2 = CLKRC = 100kHz	-	0.16	-	mA	T <sub>A</sub> = +25°C
1	I <sub>CCRCL</sub>	Iccrcl	Flash 0 wait (CLKMC, CLKPLL and CLKSC stopped)	-	-	3.5	mA	T <sub>A</sub> = +105°C
			Sub Run mode with CLKS1/2 = CLKB = CLKP1/2 = 32kHz	-	0.1	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCSUB</sub>		Flash 0 wait  (CLKMC, CLKPLL and CLKRC stopped)	-	-	3.3	mA	T <sub>A</sub> = +105°C
			PLL Sleep mode with	-	9.5	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCSPLL</sub>		CLKS1/2 = CLKP1/2 = 32MHz (CLKRC and CLKSC stopped)	-	-	15	mA	T <sub>A</sub> = +105°C
		-	Main Sleep mode with CLKS1/2 = CLKP1/2 = 4MHz, SMCR:LPMSS =	-	1.1	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCSMAIN</sub>		0 (CLKPLL, CLKRC and CLKSC stopped)	-	-	4.7	mA	T <sub>A</sub> = +105°C
Power supply		Vcc	RC Sleep mode with CLKS1/2 =	1	0.6	1	mA	T <sub>A</sub> = +25°C
modes <sup>[1]</sup> SMCR:LPMSS = 0 (CLKMC, CLKPLL and CLKSC stopped)  RC Sleep mode with CLKS1/2 =		SMCR:LPMSS = 0 (CLKMC,	-	-	4.1	mA	T <sub>A</sub> = +105°C	
		-	0.07	-	mA	T <sub>A</sub> = +25°C		
	I <sub>CCSRCL</sub>		CLKP1/2 = CLKRC = 100kHz (CLKMC, CLKPLL and CLKSC stopped)	1	-	2.9	mA	T <sub>A</sub> = +105°C
			Sub Sleep mode with CLKS1/2 = CLKP1/2 = 32kHz,	-	0.04	-	mA	T <sub>A</sub> = +25°C
	I <sub>CCSSUB</sub>		(CLKMC, CLKPLL and CLKRC stopped)	-	-	2.7	mA	T <sub>A</sub> = +105°C



		Pin	<u> </u>		Value			
Parameter	Symbol	Name	Conditions	Min	Тур	Max	Unit	Remarks
			PLL Timer mode with CLKPLL =	-	1800	2250	μΑ	T <sub>A</sub> = +25°C
	I <sub>CCTPLL</sub>		32MHz (CLKRC and CLKSC stopped)	-	-	3220	μΑ	T <sub>A</sub> = +105°C
			Main Timer mode with CLKMC = 4MHz, SMCR:LPMSS = 0 (CLKPLL,	-	285	330	μA	T <sub>A</sub> = +25°C
	I <sub>CCTMAIN</sub>		CLKRC and CLKSC stopped)	-	-	1200	μA	T <sub>A</sub> = +105°C
Power supply current in Timer		\/	RC Timer mode with CLKRC = 2MHz, SMCR:LPMSS = 0 (CLKPLL,	-	160	215	μA	T <sub>A</sub> = +25°C
modes <sup>[2]</sup>	I <sub>CCTRCH</sub>	Vcc	CLKMC and CLKSC stopped)	-	-	1110	μΑ	T <sub>A</sub> = +105°C
	I <sub>CCTRCL</sub>		RC Timer mode with CLKRC = 100kHz, (CLKPLL, CLKMC and	-	35	75	μΑ	T <sub>A</sub> = +25°C
	CCTRCL		CLKSC stopped)	-	-	910	μΑ	T <sub>A</sub> = +105°C
			Sub Timer mode with CLKSC = 32kHz (CLKMC, CLKPLL and	-	25	65	μΑ	T <sub>A</sub> = +25°C
	I <sub>CCTSUB</sub>		CLKRC stopped)	-	-	885	μА	T <sub>A</sub> = +105°C
Power supply				-	20	60	μA	T <sub>A</sub> = +25°C
current in Stop mode <sup>[3]</sup>	I <sub>CCH</sub>		-	-	-	880	μA	T <sub>A</sub> = +105°C
Flash Power Down current	I <sub>CCFLASHP</sub>		-	-	36	70	μA	
Power supply current		Vcc		-	5	-	μΑ	T <sub>A</sub> = +25°C
for active Low Voltage detector <sup>[4]</sup>	I <sub>CCLVD</sub>		Low voltage detector enabled		-	12.5	μА	T <sub>A</sub> = +105°C
Flash Write/				-	12.5	-	mA	T <sub>A</sub> = +25°C
Erase current <sup>[5]</sup>	I <sub>CCFLASH</sub>		-	-	-	20	mA	T <sub>A</sub> = +105°C

[1]: The power supply current is measured with a 4MHz external clock connected to the Main oscillator and a 32kHz external clock connected to the Sub oscillator. See chapter "Standby mode and voltage regulator control circuit" of the Hardware Manual for further details about voltage regulator control. Current for "On Chip Debugger" part is not included. Power supply current in Run mode does not include Flash Write / Erase current.

[2]: The power supply current in Timer mode is the value when Flash is in Power-down / reset mode.

When Flash is not in Power-down / reset mode, Iccflashpd must be added to the Power supply current.

The power supply current is measured with a 4MHz external clock connected to the Main oscillator and a 32 kHz external clock connected to the Sub oscillator. The current for "On Chip Debugger" part is not included.

[3]: The power supply current in Stop mode is the value when Flash is in Power-down / reset mode.

When Flash is not in Power-down / reset mode, ICCFLASHPD must be added to the Power supply current.

- [4]: When low voltage detector is enabled, ICCLVD must be added to Power supply current.
- [5]: When Flash Write / Erase program is executed, IccFLASH must be added to Power supply current.



## 14.3.2 Pin Characteristics

			AVSS = DVSS = UV, TA =		Value			
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks
	V	Port inputs	-	V <sub>cc</sub> ×0.7	-	V <sub>CC</sub> + 0.3	V	CMOS Hysteresis input
	V <sub>IH</sub>	Pnn_m	-	V <sub>CC</sub> ×0.8	ı	V <sub>CC</sub> + 0.3	V	AUTOMOTIVE Hysteresis input
	V <sub>IHX0S</sub>	X0	External clock in "Fast Clock Input mode"	VD×0.8	-	VD	V	VD=1.8V±0.15V
"H" level input voltage	V <sub>IHX0AS</sub>	X0A	External clock in "Oscillation mode"	V <sub>CC</sub> ×0.8	-	V <sub>CC</sub> + 0.3	V	
VIHE	V <sub>IHR</sub>	RSTX	-	V <sub>CC</sub> ×0.8	-	V <sub>CC</sub> + 0.3	V	CMOS Hysteresis input
	V <sub>IHM</sub>	MD	-	V <sub>CC</sub> - 0.3	-	V <sub>CC</sub> + 0.3	V	CMOS Hysteresis input
V <sub>IHD</sub>	V <sub>IHD</sub>	DEBUG I/F	-	2.0	-	V <sub>CC</sub> + 0.3	V	TTL Input
	V <sub>IL</sub>	Port inputs	-	V <sub>SS</sub> - 0.3	-	V <sub>CC</sub> ×0.3	V	CMOS Hysteresis input
	VIL	Pnn_m	-	V <sub>SS</sub> - 0.3	-	V <sub>CC</sub> ×0.5	V	AUTOMOTIVE Hysteresis input
	V <sub>ILX0S</sub>	X0	External clock in "Fast Clock Input mode"	V <sub>SS</sub>	-	VD×0.2	V	VD=1.8V±0.15V
"L" level input voltage	V <sub>ILX0AS</sub>	X0A	External clock in "Oscillation mode"	V <sub>SS</sub> - 0.3	-	V <sub>CC</sub> ×0.2	V	
	V <sub>ILR</sub>	RSTX	-	V <sub>SS</sub> - 0.3	-	V <sub>CC</sub> ×0.2	V	CMOS Hysteresis input
	V <sub>ILM</sub>	MD	-	V <sub>SS</sub> - 0.3	-	V <sub>SS</sub> + 0.3	V	CMOS Hysteresis input
	V <sub>ILD</sub>	DEBUG I/F	-	V <sub>SS</sub> - 0.3	-	0.8	V	TTL Input



					Value				
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks	
	V	4m A tuno	$4.5V \le (D)V_{CC} \le 5.5V$ $I_{OH} = -4mA$	(D))/ 0.5	-	(D))/	V		
	V <sub>OH30</sub> H	4mA type	$2.7V \le (D)V_{CC} < 4.5V$ $I_{OH} = -1.5mA$	(D)V <sub>CC</sub> - 0.5	-	(D)V <sub>CC</sub>	V		
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OH} = -52mA$		-			T 40°C	
			$2.7V \le DV_{CC} < 4.5V$ $I_{OH} = -18\text{mA}$					T <sub>A</sub> = -40°C	
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OH} = -39mA$					T <sub>A</sub> = +25°C	
"H" level		High Drive type	$2.7V \le DV_{CC} < 4.5V$ $I_{OH} = -16\text{mA}$	- DV <sub>cc</sub> - 0.5		DV <sub>cc</sub>	V		
output voltage	V OH30		$4.5V \le DV_{CC} \le 5.5V$ $I_{OH} = -32mA$					T <sub>A</sub> = +85°C	
			$2.7V \le DV_{CC} < 4.5V$ $I_{OH} = -14.5 \text{mA}$					1 <sub>A</sub> = +85 C	
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OH} = -30\text{mA}$					T <sub>A</sub> = +105°C	
			$2.7V \le DV_{CC} < 4.5V$ $I_{OH} = -14mA$					14 - 1100 0	
	V <sub>ОНЗ</sub>	3mA type	$4.5V \le V_{CC} \le 5.5V$ $I_{OH} = -3mA$	V <sub>cc</sub> - 0.5	-	Vas	V		
	v OH3	onin type	$2.7V \le V_{CC} < 4.5V$ $I_{OH} = -1.5mA$	V00- 0.0		V <sub>cc</sub>	V		



					Value			
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks
	V	4m A tum a	$4.5V \le (D)V_{CC} \le 5.5V$ $I_{OL} = +4mA$	_	_	0.4	V	
	V <sub>OL4</sub>	4mA type	$2.7V \le (D)V_{CC} < 4.5V$ $I_{OL} = +1.7mA$			0.4	v	
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OL} = +52mA$					T <sub>A</sub> = -40°C
			$2.7V \le DV_{CC} < 4.5V$ $I_{OL} = +22mA$					14 10 0
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OL} = +39mA$					T <sub>A</sub> = +25°C
"L" level	V <sub>OL30</sub>	High Drive	$2.7V \le DV_{CC} < 4.5V$ $I_{OL} = +18\text{mA}$		_	0.5	V	
output voltage	out voltage	type*	$4.5V \le DV_{CC} \le 5.5V$ $I_{OL} = +32mA$					T <sub>A</sub> = +85°C
			$2.7V \le DV_{CC} < 4.5V$ $I_{OL} = +14\text{mA}$					
			$4.5V \le DV_{CC} \le 5.5V$ $I_{OL} = +30mA$					T <sub>A</sub> = +105°C
			$2.7V \le DV_{CC} < 4.5V$ $I_{OL} = +13.5\text{mA}$					
	V <sub>OL3</sub>	3mA type	$2.7V \le V_{CC} < 5.5V$ $I_{OL} = +3mA$	-	-	0.4	V	
	V <sub>OLD</sub>	DEBUG I/F	$V_{CC} = 2.7V$ $I_{OL} = +25\text{mA}$	0	-	0.25	V	
Input leak		Pnn_m	$V_{SS} < V_I < V_{CC}$ $AV_{SS}$ , $AVRL < V_I <$ $AV_{CC}$ , $AVRH$	- 1	-	+ 1	μA	Single port pin except high current output I/O for SMC
current	I <sub>IL</sub>	P08_m, P09_m, P10_m	$\begin{aligned} & DV_{SS} < V_{I} < DV_{CC} \\ & AV_{SS,} AVRL < V_{I} < AV_{CC}, \\ & AVRH \end{aligned}$	- 3	-	+3	μA	
Total LCD leak current	Σ I <sub>ILCD</sub>	All SEG/ COM pin	V <sub>CC</sub> = 5.0V	-	0.5	10	μA	Maximum leakage current of all LCD pins
Internal LCD divide resistance	R <sub>LCD</sub>	Between V3 and V2, V2 and V1, V1 and V0	V <sub>CC</sub> = 5.0V	6.25	12.5	25	kΩ	
Pull-up resistance value	R <sub>PU</sub>	Pnn_m	V <sub>CC</sub> = 5.0V ±10%	25	50	100	kΩ	
Pull-down resistance value	R <sub>DOWN</sub>	P08_m, P09_m, P10_m	V <sub>CC</sub> = 5.0V ±10%	25	50	100	kΩ	



_			<u> </u>		Value		1114	
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks
Input capacitance	C <sub>IN</sub>	Other than C, Vcc, Vss, DVcc, DVss, AVcc, AVss, AVRH, AVRL, P08_m, P10_m	-	-	5	15	pF	
		P08_m, P09_m, P10_m	-	-	15	30	pF	


<sup>\*:</sup> In the case of driving stepping motor directly or high current outputs, set "1" to the bit in the Port High Drive Register (PHDRnn:HDx="1").



## 14.4 AC Characteristics

## 14.4.1 Main Clock Input Characteristics


(VCC = AVCC = DVCC = 2.7V		Pin		Value			,
Parameter	Symbol	Name	Min	Тур	Max	Unit	Remarks
			4	ı	8	MHz	When using a crystal oscillator, PLL off
Input frequency	f <sub>C</sub>	X0, X1	-	-	8	MHz	When using an opposite phase external clock, PLL off
1			4	ı	8	MHz	When using a crystal oscillator or opposite phase external clock, PLL on
Input frequency	f <sub>FCI</sub>	X0	-	-	8	MHz	When using a single phase external clock in "Fast Clock Input mode", PLL off
input frequency			4	-	8	MHz	When using a single phase external clock in "Fast Clock Input mode", PLL on
Input clock cycle	t <sub>CYLH</sub>	-	125	-	-	ns	
Input clock pulse width	P <sub>WH</sub> , P <sub>WL</sub>	-	55	-	-	ns	






# 14.4.2 Sub Clock Input Characteristics

B	0	Din Nama	0		Value		Unit	Damada
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks
			•	ı	32.768	ı	kHz	When using an oscillation circuit
Input frequency	f <sub>CL</sub>	X0A, X1A	-	ı	ı	100	kHz	When using an opposite phase external clock
		XOA	-	ı	ı	50	kHz	When using a single phase external clock
Input clock cycle	t <sub>CYLL</sub>	-	-	10	-	-	μs	
Input clock pulse width	-	-	P <sub>WH</sub> /t <sub>CYLL</sub> , P <sub>WL</sub> /t <sub>CYLL</sub>	30	-	70	%	







#### 14.4.3 Built-in RC Oscillation Characteristics

 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C)$ 

	Symbol		Value			
Parameter		Min	Тур	Max	Unit	Remarks
Clock from tone	4	50	100	200	kHz	When using slow frequency of RC oscillator
Clock frequency	f <sub>RC</sub>	1	2	4	MHz	When using fast frequency of RC oscillator
RC clock stabilization time		80	160	320	μs	When using slow frequency of RC oscillator (16 RC clock cycles)
NO CIOCK STADIIIZATION TIME	T <sub>RCSTAB</sub>	64	128	256	μs	When using fast frequency of RC oscillator (256 RC clock cycles)

#### 14.4.4 Internal Clock Timing


P	Ol	Va	1114	
Parameter	Symbol	Min	Max	Unit
Internal System clock frequency (CLKS1 and CLKS2)	f <sub>CLKS1</sub> , f <sub>CLKS2</sub>	-	54	MHz
Internal CPU clock frequency (CLKB), Internal peripheral clock frequency (CLKP1)	f <sub>CLKB</sub> , f <sub>CLKP1</sub>	-	32	MHz
Internal peripheral clock frequency (CLKP2)	f <sub>CLKP2</sub>	-	32	MHz



## 14.4.5 Operating Conditions of PLL


 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C)$ 

	0		Value		1114	D
Parameter	Symbol	Min	Тур	Max	Unit	Remarks
PLL oscillation stabilization wait time	t <sub>LOCK</sub>	1	-	4	ms	For CLKMC = 4MHz
PLL input clock frequency	f <sub>PLLI</sub>	4	-	8	MHz	
PLL oscillation clock frequency	f <sub>CLKVCO</sub>	56	-	108	MHz	Permitted VCO output frequency of PLL (CLKVCO)
PLL phase jitter	t <sub>PSKEW</sub>	-5	-	+5	ns	For CLKMC (PLL input clock) ≥ 4MHz



## 14.4.6 Reset Input


Dovometer	Symbol	Din Name	Valu	l lmit		
Parameter	Symbol	Pin Name	Min	Max	Unit	
Reset input time		Detv	10	=	μs	
Rejection of reset input time	TRSTL	RSTX	1	-	μs	





## 14.4.7 Power-on Reset Timing

		5' 11	Value			
Parameter	Symbol	Pin Name	Min	Тур	Max	Unit
Power on rise time	t <sub>R</sub>	Vcc	0.05	-	30	ms
Power off time	t <sub>OFF</sub>	Vcc	1	-	-	ms





#### 14.4.8 USART Timing

 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C, C_L = 50pF)$ 

Parameter	Symbol	Pin	Condition	4.5V ≤ V <sub>CC</sub> <	5.5V	2.7V ≤ V <sub>CC</sub> < 4	.5V	Unit	
Parameter	Symbol	Name	s	Min	Max	Min	Max	Offic	
Serial clock cycle time	t <sub>SCYC</sub>	SCKn		4t <sub>CLKP1</sub>	-	4t <sub>CLKP1</sub>	-	ns	
$\begin{array}{c} SCK\downarrow\toSOT\;delay\\ time \end{array}$	t <sub>SLOVI</sub>	SCKn, SOTn		- 20	+ 20	- 30	+ 30	ns	
$\begin{array}{c} SOT \to SCK \uparrow delay \\ time \end{array}$	t <sub>ovshi</sub>	SCKn, SOTn	Internal shift clock	N×t <sub>CLKP1</sub> - 20*	-	N×t <sub>CLKP1</sub> -30*	-	ns	
SIN →SCK ↑setup time	t <sub>IVSHI</sub>	SCKn, SINn	mode	t <sub>CLKP1</sub> + 45	-	t <sub>CLKP1</sub> + 55	-	ns	
$SCK \uparrow \rightarrow SIN \text{ hold time}$	t <sub>SHIXI</sub>	SCKn, SINn		0	-	0	-	ns	
Serial clock "L" pulse width	t <sub>SLSH</sub>	SCKn		t <sub>CLKP1</sub> + 10	-	t <sub>CLKP1</sub> + 10	-	ns	
Serial clock "H" pulse width	t <sub>SHSL</sub>	SCKn			t <sub>CLKP1</sub> + 10	-	t <sub>CLKP1</sub> + 10	-	ns
$\begin{array}{c} SCK\downarrow\toSOT\;delay\\ time \end{array}$	t <sub>SLOVE</sub>	SCKn, SOTn	External	-	2t <sub>CLKP1</sub> + 45	-	2t <sub>CLKP1</sub> + 55	ns	
SIN →SCK ↑setup time	t <sub>IVSHE</sub>	SCKn, SINn	shift clock mode	t <sub>CLKP1</sub> /2+ 10	-	t <sub>CLKP1</sub> /2+ 10	-	ns	
$SCK \uparrow \rightarrow SIN$ hold time	t <sub>SHIXE</sub>	SCKn, SINn		t <sub>CLKP1</sub> + 10	-	t <sub>CLKP1</sub> + 10	-	ns	
SCK fall time	t <sub>F</sub>	SCKn		-	20	-	20	ns	
SCK rise time	t <sub>R</sub>	SCKn		-	20	-	20	ns	

#### Notes:

- -AC characteristic in CLK synchronized mode.
- $-C_L$  is the load capacity value of pins when testing.
- -Depending on the used machine clock frequency, the maximum possible baud rate can be limited by some parameters. These parameters are shown in "CY96600 series HARDWARE MANUAL".
- -tclkP1 indicates the peripheral clock 1 (CLKP1), Unit: ns
- -These characteristics only guarantee the same relocate port number.

For example, the combination of SCKn and SOTn\_R is not guaranteed.


- \*: Parameter N depends on t<sub>SCYC</sub> and can be calculated as follows:
- If  $t_{SCYC} = 2 \times k \times t_{CLKP1}$ , then N = k, where k is an integer > 2
- If  $t_{SCYC} = (2 \times k + 1) \times t_{CLKP1}$ , then N = k + 1, where k is an integer > 1


#### Examples:

tscyc	N
4 xtclkp1	2
5 xtclkp1, 6 xtclkp1	3
7 xtclkp1, 8 xtclkp1	4

Document Number: 002-04717 Rev. \*D Page 49 of 73










## 14.4.9 External Input Timing

		D: N	Value			
Parameter	Symbol	Pin Name	Min	Max	Unit	Remarks
		Pnn_m		-		General Purpose I/O
		ADTG			ns	A/D Converter trigger input
		TINn				Reload Timer
		TTGn	2t <sub>CLKP1</sub> +200 (t <sub>CLKP1</sub> =1/f <sub>CLKP1</sub> )*			PPG trigger input
Input pulse width	t <sub>INH</sub> , t <sub>INL</sub>	FRCKn,				Free-Running Timer input
		FRCKn_R				clock
		INn, INn_R				Input Capture
		INTn, INTn_R	200		20	External Interrupt
		NMI	200	-	ns	Non-Maskable Interrupt

<sup>\*:</sup> tclkp1 indicates the peripheral clock1 (CLKP1) cycle time except stop when in stop mode.






#### 14.4.10 PC Timing

		<b>6</b> 11	Typic	cal Mode	High-Spe		
Parameter	Symbol	Conditions	Min	Max	Min	Max	Unit
SCL clock frequency	f <sub>SCL</sub>		0	100	0	400	kHz
(Repeated) START condition hold time SDA $\downarrow \rightarrow$ SCL $\downarrow$	t <sub>HDSTA</sub>		4.0	-	0.6	-	μs
SCL clock "L" width	t <sub>LOW</sub>		4.7	-	1.3	-	μs
SCL clock "H" width	t <sub>HIGH</sub>		4.0	-	0.6	-	μs
(Repeated) START condition setup time SCL $\uparrow \rightarrow$ SDA $\downarrow$	t <sub>SUSTA</sub>	$C_L = 50pF$ ,	4.7	-	0.6	-	μs
Data hold time		$R = (Vp/I_{OL})^{[1]}$	0	3.45 <sup>[2]</sup> 50 -	0	0.9[3]	μs
$SCL \downarrow \rightarrow SDA \downarrow \uparrow$	t <sub>HDDAT</sub>						
Data setup time			050				
$SDA \downarrow \uparrow \rightarrow SCL \uparrow$	t <sub>SUDAT</sub>		250		100	-	ns
STOP condition setup time SCL $\uparrow \rightarrow$ SDA $\uparrow$	t <sub>SUSTO</sub>		4.0	-	0.6	-	μs
Bus free time between "STOP condition" and "START condition"	t <sub>BUS</sub>		4.7	-	1.3	-	μs
Pulse width of spikes which will be suppressed by input noise filter	t <sub>SP</sub>	-	0	(1-1.5) ×t <sub>CLKP1</sub> <sup>[5]</sup>	0	(1-1.5) ×t <sub>CLKP1</sub> <sup>[5]</sup>	ns

- [1]: R and  $C_L$  represent the pull-up resistance and load capacitance of the SCL and SDA lines, respectively. Vp indicates the power supply voltage of the pull-up resistance and  $I_{OL}$  indicates  $V_{OL}$  guaranteed current.
- [2]: The maximum thddat only has to be met if the device does not extend the "L" width (tLOW) of the SCL signal.
- [3]: A high-speed mode  $I^2C$  bus device can be used on a standard mode  $I^2C$  bus system as long as the device satisfies the requirement of " $t_{SUDAT} \ge 250 ns$ ".
- [4]: For use at over 100 kHz, set the peripheral clock1 (CLKP1) to at least 6 MHz.
- [5]: t<sub>CLKP1</sub> indicates the peripheral clock1 (CLKP1) cycle time.





## 14.5 A/D Converter

#### 14.5.1 Electrical Characteristics for the A/D Converter

D	2.7V to 5.8 Symb	Pin		Value			D
Parameter	ol	Name	Min	Тур	Max	Unit	Remarks
Resolution	-	-	-	-	10	bit	
Total error	-	-	- 3.0	-	+ 3.0	LSB	
Nonlinearity error	-	-	- 2.5	-	+ 2.5	LSB	
Differential Nonlinearity error	-	-	- 1.9	-	+ 1.9	LSB	
Zero transition voltage	V <sub>OT</sub>	ANn	Typ - 20	AVRL+ 0.5LSB	Typ + 20	mV	
Full scale transition voltage	V <sub>FST</sub>	ANn	Тур - 20	AVRH- 1.5LSB	Typ + 20	mV	
Compare time*			1.0	-	5.0	μs	$4.5V \le AV_{CC} \le 5.5V$
Compare time*	-	-	2.2	-	8.0	μs	2.7V ≤ AV <sub>CC</sub> < 4.5V
Compling time*			0.5	-	-	μs	4.5V ≤ AV <sub>CC</sub> ≤ 5.5V
Sampling time*	-	-	1.2	-	-	μs	2.7V ≤ AV <sub>CC</sub> < 4.5V
	I <sub>A</sub>		-	2.0	3.1	mA	A/D Converter active
Power supply current	I <sub>AH</sub>	AV <sub>CC</sub>	-	-	3.3	μA	A/D Converter not operated
Reference power supply current	I <sub>R</sub>	AVRH	-	520	810	μΑ	A/D Converter active
(between AVRH and AVRL)	I <sub>RH</sub>	AVNII	-	-	1.0	μΑ	A/D Converter not operated
Analog input capacity	C <sub>VIN</sub>	AN2 to 4, 6 to 8, 10 to 12, 14, 15	-	-	16.0	pF	Normal outputs
		AN16 to 31	-	-	17.8	pF	High current outputs
Analog impodonos	В	ANn	-	-	2050	Ω	4.5V ≤ AV <sub>CC</sub> ≤ 5.5V
Analog impedance	R <sub>VIN</sub>	AINII	-	-	3600	Ω	2.7V ≤ AV <sub>CC</sub> < 4.5V
Analog port input current (during	I <sub>AIN</sub>	AN2 to 4, 6 to 8, 10 to 12, 14, 15	- 0.3	-	+ 0.3	μΑ	AV <sub>SS</sub> , AVRL < V <sub>AIN</sub> < AV <sub>CC</sub> , AVRH
conversion)		AN16 to 31	- 3.0	-	+ 3.0	μA	
Analog input voltage	V <sub>AIN</sub>	ANn	AVRL	-	AVRH	V	
Reference voltage	-	AVRH	AV <sub>CC</sub> - 0.1	-	AV <sub>CC</sub>	V	
range	-	AVRL	AV <sub>SS</sub>	-	AV <sub>SS</sub> + 0.1	V	
Variation between channels	-	ANn	-	-	4.0	LSB	


<sup>\*:</sup> Time for each channel.



#### 14.5.2 Accuracy and Setting of the A/D Converter Sampling Time

If the external impedance is too high or the sampling time too short, the analog voltage charged to the internal sample and hold capacitor is insufficient, adversely affecting the A/D conversion precision.

To satisfy the A/D conversion precision, a sufficient sampling time must be selected. The required sampling time (Tsamp) depends on the external driving impedance  $R_{ext}$ , the board capacitance of the A/D converter input pin  $C_{ext}$  and the AV<sub>CC</sub> voltage level. The following replacement model can be used for the calculation:



Rext: External driving impedance

Cext: Capacitance of PCB at A/D converter input

CVIN: Analog input capacity (I/O, analog switch and ADC are contained)

R<sub>VIN</sub>: Analog input impedance (I/O, analog switch and ADC are contained)

The following approximation formula for the replacement model above can be used:


 $T_{samp} = 7.62 \times (R_{ext} \times C_{ext} + (R_{ext} + R_{VIN}) \times C_{VIN})$ 

- Do not select a sampling time below the absolute minimum permitted value. (0.5µs for 4.5V ≤ AV<sub>CC</sub> ≤ 5.5V, 1.2µs for 2.7V ≤ AV<sub>CC</sub> < 4.5V)</p>
- If the sampling time cannot be sufficient, connect a capacitor of about 0.1µF to the analog input pin.
- A big external driving impedance also adversely affects the A/D conversion precision due to the pin input leakage current IIL (static current before the sampling switch) or the analog input leakage current IAIN (total leakage current of pin input and comparator during sampling). The effect of the pin input leakage current IIL cannot be compensated by an external capacitor.
- The accuracy gets worse as |AVRH AVRL| becomes smaller.




#### 14.5.3 Definition of A/D Converter Terms

- Resolution : Analog variation that is recognized by an A/D converter.
- Nonlinearity error : Deviation of the actual conversion characteristics from a straight line that connects the zero transition point (0b0000000000 ←→ 0b000000001) to the full-scale transition point (0b1111111110 ←→ 0b1111111111).
- Differential nonlinearity error: Deviation from the ideal value of the input voltage that is required to change the output code by 1LSB.
- Total error : Difference between the actual value and the theoretical value. The total error includes zero transition error, full-scale transition error and nonlinearity error.
- Zero transition voltage: Input voltage which results in the minimum conversion value.
- Full scale transition voltage: Input voltage which results in the maximum conversion value.










# 14.6 High Current Output Slew Rate

 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C)$ 

		D: 11 0 11/1			Value	·			
Parameter	Symbol	Pin Name	Conditions	Min	Тур	Max	Unit	Remarks	
Output rise/fall time	t <sub>R30</sub> , t <sub>F30</sub>	P08_m, P09_m, P10_m	Outputs driving strength set to "30mA"	15	-	75	ns	C <sub>L</sub> =85pF	



#### 14.7 Low Voltage Detection Function Characteristics


 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}\text{C to } + 105^{\circ}\text{C})$ 


				Value				
Parameter	Symbol	Ol Conditions		Тур	Max	Unit		
	V <sub>DL0</sub>	CILCR:LVL = 0000 <sub>B</sub>	2.70	2.90	3.10	V		
	V <sub>DL1</sub>	CILCR:LVL = 0001 <sub>B</sub>	2.79	3.00	3.21	V		
	V <sub>DL2</sub>	CILCR:LVL = 0010 <sub>B</sub>	2.98	3.20	3.42	V		
Detected voltage <sup>[1]</sup>	V <sub>DL3</sub>	CILCR:LVL = 0011 <sub>B</sub>	3.26	3.50	3.74	V		
	V <sub>DL4</sub>	CILCR:LVL = 0100 <sub>B</sub>	3.45	3.70	3.95	V		
V <sub>DL5</sub>		CILCR:LVL = 0111 <sub>B</sub>	3.73	4.00	4.27	V		
	V <sub>DL6</sub>	CILCR:LVL = 1001 <sub>B</sub>	3.91	4.20	4.49	V		
Power supply voltage change rate <sup>[2]</sup>	dV/dt	-	- 0.004	-	+ 0.004	V/µs		
		CILCR:LVHYS=0	-	-	50	mV		
Hysteresis width	V <sub>HYS</sub>	CILCR:LVHYS=1	80	100	120	mV		
Stabilization time	T <sub>LVDSTAB</sub>	-	-	-	75	μs		
Detection delay time	t <sub>d</sub>	-	-	-	30	μs		


<sup>[1]:</sup> If the power supply voltage fluctuates within the time less than the detection delay time (t<sub>d</sub>), there is a possibility that the low voltage detection will occur or stop after the power supply voltage passes the detection range.

<sup>[2]:</sup> In order to perform the low voltage detection at the detection voltage ( $V_{DLX}$ ), be sure to suppress fluctuation of the power supply voltage within the limits of the change ration of power supply voltage.











#### 14.8 Flash Memory Write/Erase Characteristics

 $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C)$ 

		0 1111		Value	·			
Parameter		Conditions	Min	Тур	Max	Unit	Remarks	
	Large Sector	-	-	1.6	7.5	s		
Sector erase time	Small Sector	-	-	0.4	2.1	s	Includes write time prior to internal erase.	
	Security Sector	-	-	0.31	1.65	s	internal crase.	
Word (16-bit) write time		-	-	25	400	μs	Not including system-level overhead time.	
Chip erase time		-	-	8.31	40.05	s	Includes write time prior to internal erase.	

#### Note:

While the Flash memory is written or erased, shutdown of the external power ( $V_{CC}$ ) is prohibited. In the application system where the external power ( $V_{CC}$ ) might be shut down while writing or erasing, be sure to turn the power off by using a low voltage detection function.

To put it concrete, change the external power in the range of change ration of power supply voltage  $(-0.004V/\mu s)$  to  $+0.004V/\mu s$ ) after the external power falls below the detection voltage  $(V_{DLX})^{[1]}$ .

#### Write/Erase cycles and data hold time

Write/Erase Cycles (Cycle)	Data Hold Time (Year)
1,000	20 <sup>[2]</sup>
10,000	10 <sup>[2]</sup>
100,000	5 <sup>[2]</sup>

[1]: See "14.7 Low Voltage Detection Function Characteristics".


[2]: This value comes from the technology qualification (using Arrhenius equation to translate high temperature measurements into normalized value at + 85°C).




# 15. Example Characteristics

This characteristic is an actual value of the arbitrary sample. It is not the guaranteed value.


#### ■ CY96F696
















Mode	Selected Source Clock	Clock/Regulator and FLASH Settings
Run mode	PLL	CLKS1 = CLKS2 = CLKB = CLKP1 = CLKP2 = 32MHz
	Main osc.	CLKS1 = CLKS2 = CLKB = CLKP1 = CLKP2 = 4MHz
	RC clock fast	CLKS1 = CLKS2 = CLKB = CLKP1 = CLKP2 = 2MHz
	RC clock slow	CLKS1 = CLKS2 = CLKB = CLKP1 = CLKP2 = 100kHz
	Sub osc.	CLKS1 = CLKS2 = CLKB = CLKP1 = CLKP2 = 32kHz
Sleep mode	PLL	CLKS1 = CLKS2 = CLKP1 = CLKP2 = 32MHz
oloop modo		Regulator in High Power Mode,
		(CLKB is stopped in this mode)
	Main osc.	CLKS1 = CLKS2 = CLKP1 = CLKP2 = 4MHz
		Regulator in High Power Mode,
		(CLKB is stopped in this mode)
	RC clock fast	CLKS1 = CLKS2 = CLKP1 = CLKP2 = 2MHz
	110 0100111001	Regulator in High Power Mode,
		(CLKB is stopped in this mode)
	RC clock slow	CLKS1 = CLKS2 = CLKP1 = CLKP2 = 100kHz
	110 010011011	Regulator in Low Power Mode,
		(CLKB is stopped in this mode)
	Sub osc.	CLKS1 = CLKS2 = CLKP1 = CLKP2 = 32kHz
		Regulator in Low Power Mode,
		(CLKB is stopped in this mode)
	PLL	CLKMC = 4MHz, CLKPLL = 32MHz
		(System clocks are stopped in this mode)
		Regulator in High Power Mode,
		FLASH in Power-down / reset mode
	Main osc.	CLKMC = 4MHz
		(System clocks are stopped in this mode)
		Regulator in High Power Mode,
		FLASH in Power-down / reset mode
	RC clock fast	CLKMC = 2MHz
		(System clocks are stopped in this mode)
		Regulator in High Power Mode,
		FLASH in Power-down / reset mode
	RC clock slow	CLKMC = 100kHz
		(System clocks are stopped in this mode)
		Regulator in Low Power Mode,
		FLASH in Power-down / reset mode
	Sub osc.	CLKMC = 32 kHz
		(System clocks are stopped in this mode)
		Regulator in Low Power Mode,
		FLASH in Power-down / reset mode
Stop mode	stopped	(All clocks are stopped in this mode)
		Regulator in Low Power Mode,
		FLASH in Power-down / reset mode



# 16. Ordering Information

# **MCU** with CAN Controller

Part Number	Flash Memory	Package*	
CY96F693RBPMC-GS-UJE1	Flash A (96.5KB)	100-pin plastic LQFP	
C190F093RBPMC-G5-UJE1	Flash A (90.5ND)	(LQI100)	
CY96F696RBPMC-GS-UJE1	Floob A (200 FI/D)	100-pin plastic LQFP	
CY96F696RBPMC-GS-UJE2	Flash A (288.5KB)	(LQI100)	

<sup>\*:</sup> For details about package, see "Package Dimension".


## **MCU Without CAN Controller**

Part Number	Flash Memory	Package*	
CY96F693ABPMC-GS-UJE1		100-pin plastic LQFP (LQI100)	
CY96F693ABPMC-GS-UJE2	Flash A (96.5KB)		
CY96F693ABPMC-GS-UKE2			

<sup>\*:</sup> For details about package, see "Package Dimension".



# 17. Package Dimension



SYMBOL	DIMENSIONS		
STMBOL	MIN.	NOM.	MAX.
Α	_	_	1.70
A1	0.05	_	0.15
b	0.15	_	0.27
С	0.09	_	0.20
D	16.00 BSC		
D1	14.00 BSC		
е	0.50 BSC		
E	16.00 BSC		
E1	14.00 BSC		
L	0.45	0.60	0.75
L1	0.30	0.50	0.70

#### NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- ⚠DATUM PLANE H IS LOCATED AT THE BOTTOM OF THE MOLD PARTING LINE COINCIDENT WITH WHERE THE LEAD EXITS THE BODY.
- DATUM SA-B AND D TO BE DETERMINED AT DATUM PLANE H.
- TO BE DETERMINED AT SEATING PLANE C.
- ⚠DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD PROTRUSION. ALLOW ABLE PROTRUSION IS 0.25mm PRE SIDE.
  - DIMENSIONS D1 AND E1 INCLUDE MOLD MISMATCH AND ARE DETERMINED AT DATUM PLANE H.
- ⚠DETAILS OF PIN 1 IDENTIFIER ARE OPTIONAL BUT MUST BE LOCATED WITHIN THE ZONE INDICATED.
- AREGARDLESS OF THE RELATIVE SIZE OF THE UPPER AND LOWER BODY SECTIONS. DIMENSIONS D1 AND E1 ARE DETERMINED AT THE LARGEST FEATURE OF THE BODY SCALUSIVE OF MOLD FLASH AND GATE BURRS. BUT INCLUDING ANY MISMATCH BETWEEN THE UPPER AND LOWER SECTIONS OF THE MOLDER BODY.
- ⚠DIMENSION 5 DOES NOT INCLUDE DAMBAR PROTRUSION. THE DAMBAR PROTRUSION (\$) SHALL NOT CAUSE THE LEAD WIDTH TO EXCEED 5 MAXIMUM BY MORE THAN 0.08mm. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OR THE LEAD FOOT.
- 9. THESE DIMENSIONS APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.10mm AND 0.25mm FROM THE LEAD TIP.
- 10 At is defined as the distance from the seating plane to the Lowest Point of the Package Body.

002-11500 \*A

PACKAGE OUTLINE, 100 LEAD LQFP 14.0X14.0X1.7 MM LQI100 REV\*A



# 18. Major Changes

Spansion Publication Number: MB96F696-DS704-00011

Page	Section	Change Results
Revision 1	.0	•
-	-	PRELIMINARY → Data sheet
1	■FEATURES	Changed the description of "System clock"  Up to 16 MHz external clock for devices with fast clock input feature
	-	Up to 8 MHz external clock for devices with fast clock input feature  Changed the description of "Free-Running Timers" Signals an
2		interrupt on overflow Signals an interrupt on overflow, supports timer clear upon match with Output Compare (0, 4)
2		Changed the description of "LCD Controller" On-chip drivers for internal divider resistors or external divider resistors Internal divider resistors or external divider resistors
3		Changed the description of "External Interrupts" Interrupt mask and pending bit per channel Interrupt mask bit per channel
3		Changed the description of "Built-in On Chip Debugger" - Event sequencer: 2 levels - Event sequencer: 2 levels + reset
	■PRODUCT LINEUP	Added the Product
	- I NODOOT EINEOI	Changed the Remark of RLT RLT 0/1/2/3/6 Only RLT6 can be used as PPG clock source RLT 0 to 3/6
6		Changed number of the I/O Ports 77 (Dual clock mode) 79 (Single clock mode) 75 (Dual clock mode) 77 (Single clock mode)
7	■BLOCK DIAGRAM	Deleted the block of RLT6 from PPG block Changed the RLT block
9	■PIN DESCRIPTION	4ch 0/1/2/3/6 5ch  Changed the Description of PPGn_B Programmable Pulse Generator n output (8bit)  Programmable Pulse Generator n output (16bit/8bit)
13	■PIN CIRCUIT TYPE	Changed the I/O circuit type of Pin no.96 P Q
	■I/O CIRCUIT TYPE	Changed the figure of type B Changed the Remarks of type B (CMOS hysteresis input with
14		input shutdown function, $I_{OL} = 4mA$ , $I_{OH} = -4mA$ , Programmable pull-up resister) (CMOS level output ( $I_{OL} = 4mA$ , $I_{OH} = -4mA$ ), Automotive input with input shutdown function and programmable pull-up resistor)
16	1	Changed the figure of type G
19	1	Added the Type Q
21	■MEMORY MAP	Changed the START addresses of Boot-ROM 0F:E000 <sub>H</sub> 0F:C000 <sub>H</sub>
23	USER ROM MEMORY MAP FOR FLASH DEVICES	Changed the annotation Others (from DF:0200 <sub>H</sub> to DF:1FFF <sub>H</sub> ) are all mirror area of SAS-512B.
		Others (from DF:0200 <sub>H</sub> to DF:1FFF <sub>H</sub> ) is mirror area of SAS-512B.



Page	Section	Change Results
25	■INTERRUPT VECTOR TABLE	Changed the Description of CALLV0 to CALLV7 Reserved CALLV instruction Changed the Description of RESET Reserved Reset vector Changed the Description of INT9 Reserved INT9 instruction Changed the Description of EXCEPTION Reserved
26		Undefined instruction execution  Changed the Vector name of Vector number 64 PPGRLT RLT6  Changed the Description of Vector number 64  Reload Timer 6 can be used as PPG clock source  Reload Timer 6
29 to 32	■HANDLING PRECAUTIONS	Added a section
33	■HANDLING DEVICES	Added the description to "3. External clock usage" (3) Opposite phase external clock Changed the description in "7. Turn on sequence of power
35		supply to A/D converter and analog inputs" In this case, the voltage must not exceed AVRH or AV $_{\rm CC}$ In this case, AVRH must not exceed AV $_{\rm CC}$ . Input voltage for ports shared with analog input ports also must not exceed AV $_{\rm CC}$
35		Changed the description in "11. SMC power supply pins" To avoid this, V <sub>CC</sub> must always be powered on before DV <sub>CC</sub> . To avoid this, V <sub>CC</sub> must always be powered on before DV <sub>CC</sub> . DVcc/DVss must be applied when using SMC I/O pin as GPIO.
36	■ELECTRICAL CHARACTERISTICS  1. Absolute Maximum Ratings	Added the description "13. Mode Pin (MD)"  Changed the Symbol of ""L" level average overall output current"  SI <sub>OLSMCAV</sub> SI <sub>OLAVSMC</sub> Changed the Symbol of ""H" level average overall output current"
37		ΣΙ <sub>ΟΗSMCAV</sub> ΣΙ <sub>ΟΗAVSMC</sub> Changed the annotation *2 It is required that AV <sub>CC</sub> does not exceed V <sub>CC</sub> and that the voltage at the analog inputs does not exceed AV <sub>CC</sub> when the power is switched on. It is required that AV <sub>CC</sub> does not exceed V <sub>CC</sub> , DV <sub>CC</sub> and that the voltage at the analog inputs does not exceed AV <sub>CC</sub> when the power is switched on.  Changed the annotation *3 Input/Output voltages of standard ports depend on V <sub>CC</sub> . Input/Output voltages of high current ports depend on DV <sub>CC</sub> . Input/Output voltages of standard ports depend on V <sub>CC</sub> .  Changed the annotation *4 Note that if the +B input is applied during power-on, the power supply is provided from the pins and the resulting supply voltage may not be sufficient to operate the Power reset (except devices with persistent low voltage reset in internal vector mode).  Note that if the +B input is applied during power-on, the power supply is provided from the pins and the resulting supply voltage may not be sufficient to operate the Power reset.  Added the annotation *4 The DEBUG I/F pin has only a protective diode against V <sub>SS</sub> . Hence it is only permitted to input a negative clamping current (4mA). For protection against positive input voltages, use an external clamping diode which limits the input voltage to maximum 6.0V.



Page	Section	Change Results
38	2. Recommended Operating Conditions	Added the Value and Remarks to "Power supply voltage" Min: 2.0V Typ: - Max: 5.5V Remarks: Maintains RAM data in stop mode Changed the Value of "Smoothing capacitor at C pin" Typ: 1.0vE v. 1.0vE to 2.0vE
		Typ: $1.0\mu F \rightarrow 1.0\mu F$ to $3.9\mu F$ Max: $1.5\mu F \rightarrow 4.7\mu F$ Changed the Remarks of "Smoothing capacitor at C pin" Deleted "(Target value)" Added "3.9 $\mu F$ (Allowance within ± 20%)"
	3. DC Characteristics     (1) Current Rating	Deleted "(Target value)"  Added the Symbol to "Power supply current in Run modes"    Corch   Corcl     Changed the Conditions of   Copple   Command   Copple
39		supply current in Run modes" "Flash 0 wait" is added  Changed the Value of "Power supply current in Run modes" $I_{CCPLL}$ Typ: 28.5mA $\rightarrow$ 28mA ( $T_A$ = +25°C) $I_{CCMAIN}$ Typ:5mA $\rightarrow$ 3.5mA ( $T_A$ = +25°C)  Max: 10mA $\rightarrow$ 8mA ( $T_A$ = +105°C) $I_{CCSUB}$ Typ:0.5mA $\rightarrow$ 0.1mA ( $T_A$ = +25°C)  Max: 6mA $\rightarrow$ 3.3mA ( $T_A$ = +105°C)
		Added the Symbol to "Power supply current in Sleep modes"  I <sub>CCSRCH</sub> , I <sub>CCSRCL</sub> Changed the Conditions of I <sub>CCSMAIN</sub> in "Power supply current in Sleep modes" "SMCR:LPMSS=0" is added  Changed the Value of "Power supply current in Sleep modes"  I <sub>CCSPLL</sub>
40		Typ:10mA → 9.5m A ( $T_A$ = +25°C) $I_{CCSMAIN}$ Typ: 3mA → 1.1m A ( $T_A$ = +25°C)  Max: 8mA → 4.7m A ( $T_A$ = +105°C) $I_{CCSSUB}$ Typ: 0.3mA → 0.04m A ( $T_A$ = +25°C)  Max: 4.5mA → 2.7m A ( $T_A$ = +105°C)
		Added the Symbol to "Power supply current in Timer modes"  I <sub>CCTPLL</sub> Changed the Conditions of I <sub>CCTMAIN</sub> , I <sub>CCTRCH</sub> in "Power supply current in Timer modes"  "SMCR:LPMSS=0" is added
		Changed the Value of "Power supply current in Timer modes" $I_{\text{CCTMAIN}}$ Max: $355\mu\text{A} \rightarrow 330\mu\text{A}$ ( $T_{\text{A}} = +25^{\circ}\text{C}$ ) Max: $1320\mu\text{A} \rightarrow 1200\mu\text{A}$ ( $T_{\text{A}} = +105^{\circ}\text{C}$ ) $I_{\text{CCTRCH}}$ Max: $245\mu\text{A} \rightarrow 215\mu\text{A}$ ( $T_{\text{A}} = +25^{\circ}\text{C}$ )
		Max: $1230\mu A \rightarrow 215\mu A$ (T <sub>A</sub> = +25°C)  Max: $1230\mu A \rightarrow 1110\mu A$ (T <sub>A</sub> = +105°C)  I <sub>CCTRCL</sub> Max: $105\mu A \rightarrow 75\mu A$ (T <sub>A</sub> = +25°C)
		Max: 1030μA $\rightarrow$ 910μA ( $T_A = +105$ °C) $I_{CCTSUB}$ Typ: 90μA $\rightarrow$ 65μA ( $T_A = +25$ °C)
		Max: $1000\mu A \rightarrow 885\mu A \ (T_A = +105^{\circ}C)$



Page	Section	Change Results
	DC Characteristics     (1) Current Rating	Changed the Value of "Power supply current in Stop modes"
		Max: $90\mu A \rightarrow 60\mu A \ (T_A = +25^{\circ}C)$
		Max: 1000μA → 880μA (T <sub>A</sub> = +105°C)
		Added the Symbol
		CCFLASHPD   Changed the Value and condition of "Power supply current for active Low Voltage detector"   I <sub>CCLVD</sub>   Typ: 5μA, Max: 15μA, Remarks: nothing   Typ: 5μA, Max: -, Remarks: T <sub>A</sub> = +25°C
		Typ: -, Max: 12.5μA, Remarks: T <sub>A</sub> = +25 °C
41		Changed the condition of "Flash Write/Erase current"  I <sub>CCFLASH</sub> Typ: 12.5mA, Max: 20mA, Remarks: nothing Typ: 12.5mA, Max: -, Remarks: T <sub>A</sub> = +25°C Typ: -, Max: 20mA, Remarks: T <sub>A</sub> = +105°C
		Changed the annotation *2 The power supply current is measured with a 4MHz external clock connected to the Main oscillator and a 32kHz external clock connected to the Sub oscillator. When Flash is not in Power-down / reset mode, I <sub>CCFLASHPD</sub> must
		be added to the Power supply current.  The power supply current is measured with a 4MHz external clock connected to the Main oscillator and a 32kHz external clock connected to the Sub oscillator. The current for "On Chip Debugger" part is not included.
42	3. DC Characteristics	Added the Symbol for DEBUG I/F pin V <sub>OLD</sub>
43	(2) Pin Characteristics	Changed the Pin name of "Input capacitance" Other than Vcc, Vss, AVcc, AVss, AVRH, AVRL, P08_m, P09_m, P10_m Other than C, Vcc, Vss, DVcc, DVss, AVcc, AVss, AVRH, AVRL, P08_m, P09_m Deleted the annotation "I <sub>OH</sub> and I <sub>OL</sub> are target value."
		"In the case of driving stepping motor directly or high current outputs, set "1" to the bit in the Port High Drive Register (PHDRnn:HDx="1")."



Page	Section	Change Results
46	4. AC Characteristics     (1) Main Clock Input Characteristics	Changed MAX frequency for $f_{\text{FCI}}$ in all conditions $16 \rightarrow 8$ Changed MIN frequency for $t_{\text{CYLH}}$ $62.5 \rightarrow 125$ Changed MIN, MAX and Unit for $P_{\text{WH}}$ , $P_{\text{WL}}$ MIN: $30 \rightarrow 55$ MAX: $70 \rightarrow -$ Unit: $\% \rightarrow \text{ns}$
47	4. AC Characteristics     (2) Sub Clock Input Characteristics	Added the figure ( $t_{\text{CYLH}}$ ) when using the external clock Added the figure ( $t_{\text{CYLL}}$ ) when using the crystal oscillator clock
48	AC Characteristics     (3) Built-in RC Oscillation Characteristics	Added "RC clock stabilization time"
49	AC Characteristics     (5) Operating Conditions of PLL	Changed the Value of "PLL input clock frequency"  Max: 16MHz → 8MHz  Changed the Symbol of "PLL macro oscillation clock frequency"  f <sub>PLLO</sub> → f <sub>CLKVCO</sub> Added Remarks to "PLL oscillation clock frequency"  Added "PLL phase jitter" and the figure
	AC Characteristics     (6) Reset Input	Added the figure for reset input time (t <sub>RSTL</sub> )
51	4. AC Characteristics (8) USART Timing	Changed the condition $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}\text{C to } + 105^{\circ}\text{C})$ $(V_{CC} = AV_{CC} = DV_{CC} = 2.7V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}\text{C to } + 105^{\circ}\text{C}, C_L = 50\text{pF})$ Changed the HARDWARE MANUAL
		"MB96690 series HARDWARE MANUAL"  "MB96600 series HARDWARE MANUAL"
52	4. AC Characteristics	Changed the figure for "Internal shift clock mode"  Added parameter, "Noise filter" and an annotation *5 for it
54	(10) I <sup>2</sup> C timing	Added t <sub>SP</sub> to the figure
55	5. A/D Converter (1) Electrical Characteristics for the A/D Converter	Added "Analog impedance"  Added "Variation between channels"  Added the annotation
56	5. A/D Converter (2) Accuracy and Setting of the A/D Converter Sampling Time	Deleted the unit "[Min]" from approximation formula of Sampling time
	5. A/D Converter (3) Definition of A/D Converter Terms	Changed the Description and the figure "Linearity"   "Nonlinearity" "Differential linearity error" "Differential nonlinearity error"
57		Changed the Description Linearity error: Deviation of the line between the zero-transition point (0b0000000000←→0b0000000001) and the full-scale transition point (0b11111111110←→0b1111111111) from the actual conversion characteristics. Nonlinearity error:
		Deviation of the actual conversion characteristics from a straight line that connects the zero transition point (0b0000000000 ←→ 0b0000000001) to the full-scale transition point (0b11111111110 ←→ 0b1111111111).
		Added the Description "Zero transition voltage"
		"Full scale transition voltage"



Page	Section	Change Results
	6. High Current Output Slew Rate	Changed the condition
59		$(V_{CC} = AV_{CC} = 2.7V \text{ to } 5.5V, DV_{CC} = 4.5V \text{ to } 5.5V, V_{SS} = AV_{SS} = DV_{SS} = 0V, T_A = -40^{\circ}C \text{ to } + 105^{\circ}C)$
		(V <sub>CC</sub> = AV <sub>CC</sub> = DV <sub>CC</sub> = 2.7V to 5.5V, V <sub>SS</sub> = AV <sub>SS</sub> = DV <sub>SS</sub> = 0V, $T_A$ = -40°C to +105°C)
		Changed the Symbol and figure $t_{R2},t_{F2},V_{OL2}$
		$t_{R30}, t_{F30}, V_{OL30}$
	7. Low Voltage Detection Function Characteristics	Added the Value of " Power supply voltage change rate" Max: +0.004 V/μs
		Added "Hysteresis width" (V <sub>HYS</sub> )
59		Added "Stabilization time" (T <sub>LVDSTAB</sub> )
		Added "Detection delay time" (t <sub>d</sub> )
		Deleted the Remarks
		Added the annotation *1, *2
50	7. Low Voltage Detection Function	Added the figure for "Hysteresis width"
59	Characteristics	Added the figure for "Stabilization time"
	8. Flash Memory Write/Erase Characteristics	Changed the Value of "Sector erase time"
		Added "Security Sector" to "Sector erase time"
		Changed the Parameter
		"Half word (16 bit) write time"
		"Word (16-bit) write time"
61		Changed the Value of "Chip erase time"
		Changed the Remarks of "Sector erase time" Excludes write time prior to internal erase
		Includes write time prior to internal erase
		Added the Note and annotation *1
		Deleted "(targeted value)" from title "Write/Erase cycles and data hold time"
62 to 63	■EXAMPLE CHARACTERISTICS	Added a section
	ORDERING INFORMATION	Changed part number
		MCU with CAN controller
		MB96F696RAPMC-GSE1* → MB96F696RBPMC-GSE1
		MB96F696RAPMC-GSE2* → MB96F696RBPMC-GSE2
		Added part number
		MCU with CAN controller
		MB96F693RBPMC-GSE1
65		MB96F693RBPMC-GSE2
		MB96F695RBPMC-GSE1
		MB96F695RBPMC-GSE2
		MCU without CAN controller
		MB96F693ABPMC-GSE1
		MB96F693ABPMC-GSE2
		MB96F695ABPMC-GSE1
		MB96F695ABPMC-GSE2
Revision 1.1	1	
-	-	Company name and layout design change

NOTE: Please see "Document History" about later revised information.



Page	Section	Change Results		
Rev. *B				
-	Marketing Part Numbers changed from an MB pr	efix to a CY prefix.		
7, 9, 66,67	Product Lineup     Pin Assignment     Ordering Information     Package Dimension	Package description modified to JEDEC description.  FPT-100P-M20 → LQI100		
66	16. Ordering Information	Revised Marketing Part Numbers as follows:  Before)  MCU with CAN controller  MB96F693RBPMC-GSE1  MB96F693RBPMC-GSE2  MB96F695RBPMC-GSE1  MB96F696RBPMC-GSE1  MB96F696RBPMC-GSE2  MCU without CAN controller  MB96F693ABPMC-GSE1  MB96F695ABPMC-GSE1  MB96F695ABPMC-GSE1  MB96F695ABPMC-GSE1  CY96F695ABPMC-GSE1  MCU with CAN controller  CY96F693RBPMC-GS-UJE1  CY96F696RBPMC-GS-UJE1  CY96F696RBPMC-GS-UJE1  CY96F693ABPMC-GS-UJE1  CY96F693ABPMC-GS-UJE1  CY96F693ABPMC-GS-UJE1  CY96F693ABPMC-GS-UJE1  CY96F693ABPMC-GS-UJE1		
Rev. *C 63	16. Ordering Information	Added Marketing Part Number as follows: CY96F693ABPMC-GS-UKE2		



# **Document History**

Document Title: CY96690 Series, F<sup>2</sup>MC-16FX 16-Bit Proprietary Microcontroller

Document Number: 002-04717

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	-	TORS	01/31/2014	Migrated to Cypress and assigned document number 002-04717.  No change to document contents or format.
*A	5148388	TORS	09/22/2016	Updated to Cypress template.
*B	6006770	MIYH	12/28/2017	Updated Document Title to read as "CY96690 Series, F²MC-16FX 16-Bit Proprietary Microcontroller". Replaced MB96690 Series with CY96690 Series in all instances across the document. Changed the prefix of all MPNs from MB to CY in all instances across the document. Replaced FPT-100P-M20 with LQI100 in all instances across the document. Updated Ordering Information. For details, please see 18. Major Changes.
*C	6353089	SHUS	10/17/2018	Updated Ordering Information. For details, please see 18. Major Changes.
*D	6600964	TORS	06/21/2019	Updated to new template.



# Sales, Solutions, and Legal Information

#### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

#### **Products**

Arm® Cortex® Microcontrollers cypress.com/arm Automotive cypress.com/automotive Clocks & Buffers cypress.com/clocks Interface cypress.com/interface Internet of Things cypress.com/iot cypress.com/memory Memory Microcontrollers cypress.com/mcu **PSoC** cypress.com/psoc Power Management ICs cypress.com/pmic **Touch Sensing** cypress.com/touch **USB Controllers** cypress.com/usb Wireless Connectivity cypress.com/wireless

#### **PSoC® Solutions**

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6 MCU

#### **Cypress Developer Community**

Community | Projects | Video | Blogs | Training | Components

#### **Technical Support**

cypress.com/support

Arm and Cortex are registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere.

© Cypress Semiconductor Corporation, 2011-2019. This document is the property of Cypress Semiconductor Corporation and its subsidiaries ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. No computing device can be absolutely secure. Therefore, despite security measures implement on Cypress hardware or software products, Cypress shall have no liability arising out of any security breach, such as unauthorized access to or use of a Cypress product. CYPRESS DOES NOT REPRESENT, WARRANT, OR GUARANTEE THAT CYPRESS PRODUCTS, OR SYSTEMS CREATED USING CYPRESS PRODUCTS, WILL BE FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION (collectively, "Security Breach"). Cypress disclaims any liability relating to any Security Breach, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from any Security Breach. In addition, the products described in these materials may contain design defects or errors known as errata which may cause the product to deviate from published specifications. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. "High-Risk Device" means any device or system whose failure could cause personal injury, death, or property damage. Examples of High-Risk Devices are weapons, nuclear installations, surgical implants, and other medical devices. "Critical Component" means any component of

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners.

Document Number: 002-04717 Rev. \*D Revised June 21, 2019 Page 73 of 73