

# Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as "Cypress" document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

# **Continuity of document content**

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

# **Continuity of ordering part numbers**

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

www.infineon.com



# THIS SPEC IS OBSOLETE

**Spec No**: 001-85935

Spec Title: FM25H20, 2-MBIT (256 K X 8) SERIAL (SPI) F-RAM (PRELIMINARY)

Sunset Owner: Girija Chougala (GVCH)

Replaced by: None



# 2-Mbit (256 K x 8) Serial (SPI) F-RAM

#### **Features**

- 2-Mbit ferroelectric random access memory (F-RAM) logically organized as 256 K × 8
  - ☐ High-endurance 100 trillion (10<sup>14</sup>) read/writes
  - □ 151-year data retention (See the Data Retention and Endurance table)
  - □ NoDelay<sup>™</sup> writes
  - □ Advanced high-reliability ferroelectric process
- Very fast serial peripheral interface (SPI)
  - □ Up to 40-MHz frequency
  - □ Direct hardware replacement for serial flash and EEPROM
  - □ Supports SPI mode 0 (0, 0) and mode 3 (1, 1)
- Sophisticated write protection scheme
  - ☐ Hardware protection using the Write Protect (WP) pin
  - □ Software protection using Write Disable instruction
  - □ Software block protection for 1/4, 1/2, or entire array
- Low power consumption
  - □ 1 mA active current at 1 MHz
  - 80 μA (typ) standby current
  - □ 3 µA sleep mode current
- Low-voltage operation: V<sub>DD</sub> = 2.7 V to 3.6 V
- Industrial temperature -40 °C to +85 °C
- Packages
  - ☐ 8-pin small outline integrated circuit (SOIC) package
  - □ 8-pin thin dual flat no leads (TDFN) package
- Restriction of hazardous substances (RoHS) compliant

#### **Functional Overview**

The FM25H20 is a 2-Mbit nonvolatile memory employing an advanced ferroelectric process. A ferroelectric random access memory or F-RAM is nonvolatile and performs reads and writes similar to a RAM. It provides reliable data retention for 151 years while eliminating the complexities, overhead, and system-level reliability problems caused by serial flash, EEPROM, and other nonvolatile memories.


Unlike serial flash and EEPROM, the FM25H20 performs write operations at bus speed. No write delays are incurred. Data is written to the memory array immediately after each byte is successfully transferred to the device. The next bus cycle can commence without the need for data polling. In addition, the product offers substantial write endurance compared with other nonvolatile memories. The FM25H20 is capable of supporting 10<sup>14</sup> read/write cycles, or 100 million times more write cycles than EEPROM.

These capabilities make the FM25H20 ideal for nonvolatile memory applications, requiring frequent or rapid writes. Examples range from data collection, where the number of write cycles may be critical, to demanding industrial controls where the long write time of serial flash or EEPROM can cause data loss.

The FM25H20 provides substantial benefits to users of serial EEPROM or flash as a hardware drop-in replacement. The FM25H20 uses the high-speed SPI bus, which enhances the high-speed write capability of F-RAM technology. The device specifications are guaranteed over an industrial temperature range of –40 °C to +85 °C.

For a complete list of related documentation, click here.

# **Logic Block Diagram**



Cypress Semiconductor Corporation
Document Number: 001-85935 Rev. \*G



#### **Contents**

Pinouts	3
Pin Definitions	3
Overview	4
Memory Architecture	4
Serial Peripheral Interface - SPI Bus	4
SPI Overview	4
SPI Modes	5
Power Up to First Access	6
Command Structure	6
WREN - Set Write Enable Latch	6
WRDI - Reset Write Enable Latch	6
Status Register and Write Protection	7
RDSR - Read Status Register	8
WRSR - Write Status Register	8
Memory Operation	8
Write Operation	8
Read Operation	9
HOLD Pin Operation	
Sleep Mode	10
Endurance	
Maximum Ratings	12

Operating Range	12
DC Electrical Characteristics	12
Data Retention and Endurance	13
Capacitance	13
Thermal Resistance	13
AC Test Conditions	13
AC Switching Characteristics	14
Power Cycle Timing	16
Ordering Information	17
Ordering Code Definitions	17
Package Diagrams	18
Acronyms	20
Document Conventions	
Units of Measure	20
Document History Page	21
Sales, Solutions, and Legal Information	22
Worldwide Sales and Design Support	22
Products	22
PSoC® Solutions	22
Cypress Developer Community	22
Technical Support	



#### **Pinouts**

Figure 1. 8-pin SOIC pinout





Figure 2. 8-pin TDFN pinout



# **Pin Definitions**

Pin Name	I/O Type	Description	
CS	Input	Chip Select. This active LOW input activates the device. When HIGH, the device enters low-power standby mode, ignores other inputs, and the output is tristated. When LOW, the device internally activates the SCK signal. A falling edge on CS must occur before every opcode.	
SCK	Input	<b>Serial Clock</b> . All I/O activity is synchronized to the serial clock. Inputs are latched on the rising edge and outputs occur on the falling edge. Because the device is synchronous, the clock frequency may be any value between 0 and 40 MHz and may be interrupted at any time.	
SI <sup>[1]</sup>	Input	<b>Serial Input.</b> All data is input to the device on this pin. The pin is sampled on the rising edge of SCK and is ignored at other times. It should always be driven to a valid logic level to meet IDE specifications.	
SO <sup>[1]</sup>	Output	Serial Output. This is the data output pin. It is driven during a read and remains tristated at all other times including when HOLD is LOW. Data transitions are driven on the falling edge of the serial clock.	
WP	Input	<b>Write Protect</b> . This Active LOW pin prevents write operation to the Status Register when WPEI is set to '1'. This is critical because other write protection features are controlled through the Statu Register. A complete explanation of write protection is provided in "Status Register and Write Protection" on page 7. This pin must be tied to V <sub>DD</sub> if not used.	
HOLD	Input	HOLD Pin. The HOLD pin is used when the host CPU must interrupt a memory operation for another task. When HOLD is LOW, the current operation is suspended. The device ignores and transition on SCK or CS. All transitions on HOLD must occur while SCK is LOW. This pin must be tied to V <sub>DD</sub> if not used.	
V <sub>SS</sub>	Power supply	Ground for the device. Must be connected to the ground of the system.	
$V_{DD}$	Power supply	Power supply input to the device.	
EXPOSED PAD	No connect	The EXPOSED PAD on the bottom of 8-pin TDFN package is not connected to the die. The EXPOSED PAD should be left floating.	

#### Note

Document Number: 001-85935 Rev. \*G

<sup>1.</sup> SI may be connected to SO for a single pin data interface.



#### Overview

The FM25H20 is a serial F-RAM memory. The memory array is logically organized as 262,144  $\times$  8 bits and is accessed using an industry-standard serial peripheral interface (SPI) bus. The functional operation of the F-RAM is similar to serial flash and serial EEPROMs. The major difference between the FM25H20 and a serial flash or EEPROM with the same pinout is the F-RAM's superior write performance, high endurance, and low power consumption.

### **Memory Architecture**

When accessing the FM25H20, the user addresses 256K locations of eight data bits each. These eight data bits are shifted in or out serially. The addresses are accessed using the SPI protocol, which includes a chip select (to permit multiple devices on the bus), an opcode, and a three-byte address. The upper 6 bits of the address range are 'don't care' values. The complete address of 18 bits specifies each byte address uniquely.

Most functions of the FM25H20 are either controlled by the SPI interface or handled by on-board circuitry. The access time for the memory operation is essentially zero, beyond the time needed for the serial protocol. That is, the memory is read or written at the speed of the SPI bus. Unlike a serial flash or EEPROM, it is not necessary to poll the device for a ready condition because writes occur at bus speed. By the time a new bus transaction can be shifted into the device, a write operation is complete. This is explained in more detail in the interface section.

# Serial Peripheral Interface – SPI Bus

The FM25H20 is a SPI slave device and operates at speeds up to 40 MHz. This high-speed serial bus provides high-performance serial communication to a SPI master. Many common microcontrollers have hardware SPI ports allowing a direct interface. It is quite simple to emulate the port using ordinary port pins for microcontrollers that do not. The FM25H20 operates in SPI Mode 0 and 3.

#### **SPI Overview**

The SPI is a four-pin interface with Chip Select ( $\overline{CS}$ ), Serial Input (SI), Serial Output (SO), and Serial Clock (SCK) pins.

The SPI is a synchronous serial interface, which uses clock and data pins for memory access and supports multiple devices on the data bus. A device on the SPI bus is activated using the CS pin.

The relationship between chip select, clock, and data is dictated by the SPI mode. This device supports SPI modes 0 and 3. In both of these modes, data is clocked into the F-RAM on the rising edge of SCK starting from the first rising edge after  $\overline{\text{CS}}$  goes active.

The SPI protocol is controlled by opcodes. These opcodes specify the commands from the bus master to the slave device. After CS is activated, the first byte transferred from the bus

master is the opcode. Following the opcode, any addresses and data are then transferred. The  $\overline{\text{CS}}$  must go inactive after an operation is complete and before a new opcode can be issued. The commonly used terms in the SPI protocol are as follows:

#### SPI Master

The SPI master device controls the operations on a SPI bus. An SPI bus may have only one master with one or more slave devices. All the slaves share the same SPI bus lines and the master may select any of the slave devices using the  $\overline{\text{CS}}$  pin. All of the operations must be initiated by the master activating a slave device by pulling the  $\overline{\text{CS}}$  pin of the slave LOW. The master also generates the SCK and all the data transmission on SI and SO lines are synchronized with this clock.

#### SPI Slave

The SPI slave device is activated by the master through the Chip Select line. A slave device gets the SCK as an input from the SPI master and all the communication is synchronized with this clock. An SPI slave never initiates a communication on the SPI bus and acts only on the instruction from the master.

The FM25H20 operates as an SPI slave and may share the SPI bus with other SPI slave devices.

#### Chip Select (CS)

To select any slave device, the master needs to pull down the corresponding  $\overline{CS}$  pin. Any instruction can be issued to a slave device only while the  $\overline{CS}$  pin is LOW. When the device is not selected, data through the SI pin is ignored and the serial output pin (SO) remains in a high-impedance state.

**Note** A new instruction must begin with the falling edge of  $\overline{\text{CS}}$ . Therefore, only one opcode can be issued for each active Chip Select cycle.

#### Serial Clock (SCK)

The Serial Clock is generated by the SPI master  $\underline{\text{and}}$  the communication is synchronized with this clock after  $\overline{\text{CS}}$  goes LOW.

The FM25H20 enables SPI modes 0 and 3 for data communication. In both of these modes, the inputs are latched by the slave device on the rising edge of SCK and outputs are issued on the falling edge. Therefore, the first rising edge of SCK signifies the arrival of the first bit (MSB) of a SPI instruction on the SI pin. Further, all data inputs and outputs are synchronized with SCK.

#### Data Transmission (SI/SO)

The SPI data bus consists of two lines, SI and SO, for serial data communication. SI is also referred to as Master Out Slave In (MOSI) and SO is referred to as Master In Slave Out (MISO). The master issues instructions to the slave through the SI pin, while the slave responds through the SO pin. Multiple slave devices may share the SI and SO lines as described earlier.

The FM25H20 has two separate pins for SI and SO, which can be connected with the master as shown in Figure 3.



For a microcontroller that has no dedicated SPI bus, a general-purpose port may be used. To reduce hardware resources on the controller, it is possible to connect the two data pins (SI, SO) together and tie off (HIGH) the HOLD and WP pins. Figure 4 shows such a configuration, which uses only three pins.

#### Most Significant Bit (MSB)

The SPI protocol requires that the first bit to be transmitted is the Most Significant Bit (MSB). This is valid for both address and data transmission.

The 2-Mbit serial F-RAM requires a 3-byte address for any read or write operation. Because the address is only 18 bits, the first six bits, which are fed in are ignored by the device. Although these six bits are 'don't care', Cypress recommends that these bits be set to 0s to enable seamless transition to higher memory densities.

#### Serial Opcode

After the slave device is selected with  $\overline{\text{CS}}$  going LOW, the first byte received is treated as the opcode for the intended operation. FM25H20 uses the standard opcodes for memory accesses.

#### Invalid Opcode

If an invalid opcode is received, the opcode is ignored and the device ignores any <u>additional</u> serial data on the SI pin until the next falling edge of  $\overline{CS}$ , and the SO pin remains tristated.

#### Status Register

FM25H20 has an 8-bit Status Register. The bits in the Status Register are used to configure the device. These bits are described in Table 3 on page 7.





Figure 3. System Configuration with SPI Port

Figure 4. System Configuration without SPI Port



#### **SPI Modes**

FM25H20 may be driven by a microcontroller with its SPI peripheral running in either of the following two modes:

- SPI Mode 0 (CPOL = 0, CPHA = 0)
- SPI Mode 3 (CPOL = 1, CPHA = 1)

For both these modes, the input data is latched in on  $\underline{\text{the}}$  rising edge of SCK starting from the first rising edge after  $\overline{\text{CS}}$  goes active. If the clock starts from a HIGH state (in mode 3), the first rising edge after the clock toggles is considered. The output data is available on the falling edge of SCK.



The two SPI modes are shown in Figure 5 on page 6 and Figure 6 on page 6. The status of the clock when the bus master is not transferring data is:

- SCK remains at 0 for Mode 0
- SCK remains at 1 for Mode 3

The device detects the SPI mode from the status of the SCK pin when the device is selected by bringing the  $\overline{\text{CS}}$  pin LOW. If the SCK pin is LOW when the device is selected, SPI Mode 0 is assumed and if the SCK pin is HIGH, it works in SPI Mode 3.

Figure 5. SPI Mode 0





Figure 6. SPI Mode 3



#### **Power Up to First Access**

The FM25V20 is not accessible for a  $t_{PU}$  time after power-up. Users must comply with the timing parameter,  $t_{PU}$ , which is the minimum time from  $V_{DD}$  (min) to the first  $\overline{CS}$  LOW.

#### **Command Structure**

There are seven commands, called opcodes, that can be issued by the bus master to the FM25H20. They are listed in Table 1. These opcodes control the functions performed by the memory.

**Table 1. Opcode Commands** 


Name	Description	Opcode
WREN	Set write enable latch	0000 0110b
WRDI	Reset write enable latch	0000 0100b
RDSR	Read Status Register	0000 0101b
WRSR	Write Status Register	0000 0001b
READ	Read memory data	0000 0011b
WRITE	Write memory data	0000 0010b
SLEEP	Enter sleep mode	1011 1001b

#### **WREN - Set Write Enable Latch**

The FM25H20 will power up with writes disabled. The WREN command must be issued before any write operation. Sending the WREN opcode allows the user to issue subsequent opcodes for write operations. These include writing the Status Register (WRSR) and writing the memory (WRITE).

Sending the WREN opcode causes the internal Write Enable Latch to be set. A flag bit in the Status Register, called WEL, indicates the state of the latch. WEL = '1' indicates that writes are permitted. Attempting to write the WEL bit in the Status Register has no effect on the state of this bit – only the WREN opcode can set this bit. The WEL bit will be automatically cleared on the rising edge of  $\overline{CS}$  following a WRDI, a WRSR, or a WRITE operation. This prevents further writes to the Status Register or the F-RAM array without another WREN command. Figure 7 illustrates the WREN command bus configuration.


Figure 7. WREN Bus Configuration



#### WRDI - Reset Write Enable Latch

The WRDI command disables all write activity by clearing the Write Enable Latch. The user can verify that writes are disabled by reading the WEL bit in the Status Register and verifying that WEL is equal to '0'. Figure 8 illustrates the WRDI command bus configuration.

Figure 8. WRDI Bus Configuration





#### Status Register and Write Protection

The write protection features of the FM25H20 are multi-tiered and are enabled through the status register. The Status Register

is organized as follows. (The default value shipped from the factory for bit 0, WEL, BP0, BP1, bits 4–5, WPEN is '0', and for bit 6 is '1'.)

Table 2. Status Register

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
WPEN (0)	X (1)	X (0)	X (0)	BP1 (0)	BP0 (0)	WEL (0)	X (0)

Table 3. Status Register Bit Definition

Bit	Definition	Description	
Bit 0	Don't care	This bit is non-writable and always returns '0' upon read.	
Bit 1 (WEL)	Write Enable	/EL indicates if the device is write enabled. This bit defaults to '0' (disabled) on power-up /EL = '1'> Write enabled /EL = '0'> Write disabled	
Bit 2 (BP0)	Block Protect bit '0'	Used for block protection. For details, see Table 4 on page 7.	
Bit 3 (BP1)	Block Protect bit '1'	sed for block protection. For details, see Table 4 on page 7.	
Bit 4-5	Don't care	These bits are non-writable and always return '0' upon read.	
Bit 6	Don't care	This bit is non-writable and always returns '1' upon read.	
Bit 7 (WPEN)	Write Protect Enable bit	Used to enable the function of Write Protect Pin (WP). For details, see Table 5 on page 7.	

Bits 0 and 4-5 are fixed at '0' and bit 6 is fixed at '1'; none of these bits can be modified. Note that bit 0 ("Ready or Write in progress" bit in serial flash and EEPROM) is unnecessary, as the F-RAM writes in real-time and is never busy, so it reads out as a '0'. An exception to this is when the device is waking up from sleep mode, which is described in Sleep Mode on page 10. The BP1 and BP0 control the software write-protection features and are nonvolatile bits. The WEL flag indicates the state of the Write Enable Latch. Attempting to directly write the WEL bit in the Status Register has no effect on its state. This bit is internally set and cleared via the WREN and WRDI commands, respectively.

BP1 and BP0 are memory block write protection bits. They specify portions of memory that are write-protected as shown in Table 4.

**Table 4. Block Memory Write Protection** 

BP1	BP0	Protected Address Range	
0	0	None	
0	1	30000h to 3FFFFh (upper 1/4)	
1	0	20000h to 3FFFFh (upper 1/2)	
1	1	00000h to 3FFFFh (all)	

The BP1 and BP0 bits and the Write Enable Latch are the only mechanisms that protect the memory from writes. The remaining write protection features protect inadvertent changes to the block protect bits.

The write protect enable bit (WPEN) in the Status Register controls the effect of the hardware write protect  $(\overline{WP})$  pin. When the WPEN bit is set to '0', the status of the  $\overline{WP}$  pin is ignored. When the WPEN bit is set to '1', a LOW on the  $\overline{WP}$  pin inhibits a write to the Status Register. Thus the Status Register is write-protected only when WPEN = '1' and  $\overline{WP}$  = '0'.

Table 5 summarizes the write protection conditions.

Table 5. Write Protection

WEL	WPEN	WP	Protected Blocks	Unprotected Blocks	Status Register
0	Χ	Χ	Protected	Protected	Protected
1	0	Χ	Protected	Unprotected	Unprotected
1	1	0	Protected	Unprotected	Protected
1	1	1	Protected	Unprotected	Unprotected




#### **RDSR - Read Status Register**

The RDSR command allows the bus master to verify the contents of the Status Register. Reading the status register provides information about the current state of the write-protection features. Following the RDSR opcode, the FM25H20 will return one byte with the contents of the Status Register.

setting the WPEN, BP0 and BP1 bits as required. Before issuing a WRSR command, the  $\overline{\text{WP}}$  pin must be HIGH or inactive. Note that on the FM25H20,  $\overline{\text{WP}}$  only prevents writing to the Status Register, not the memory array. Before sending the WRSR command, the user must send a WREN command to enable writes. Executing a WRSR command is a write operation and therefore, clears the Write Enable Latch.

#### **WRSR - Write Status Register**

The WRSR command allows the SPI bus master to write into the Status Register and change the write protect configuration by



Opcode Data

SI 0 0 0 0 0 0 1 \( \text{D7}\times \times \times \text{X}\times \text{D3}\times \text{D2}\times \times \times \text{LSB} \\

SO HI-Z

# **Memory Operation**

The SPI interface, which is capable of a high clock frequency, highlights the fast write capability of the F-RAM technology. Unlike serial flash and EEPROMs, the FM25H20 can perform sequential writes at bus speed. No page register is needed and any number of sequential writes may be performed.

#### **Write Operation**

All writes to the memory begin with a WREN opcode with  $\overline{\text{CS}}$  being asserted and deasserted. The next opcode is WRITE. The WRITE opcode is followed by a three-byte address containing the 18-bit address (A17-A0) of the first data byte to be written into the memory. The upper six bits of the three-byte address are ignored. Subsequent bytes are data bytes, which are written sequentially. Addresses are incremented internally <u>as</u> long as the bus master continues to issue clocks and keeps  $\overline{\text{CS}}$  LOW. If

the last address of 3FFFFh is reached, the counter will roll over to 00000h. Data is written MSB first. The rising edge of  $\overline{\text{CS}}$  terminates a write operation. A write operation is shown in Figure 11.

**Note** When a burst write reaches a protected block address, the automatic address increment stops and all the subsequent data bytes received for write will be ignored by the device.

EEPROMs use page buffers to increase their write throughput. This compensates for the technology's inherently slow write operations. F-RAM memories do not have page buffers because each byte is written to the F-RAM array immediately after it is clocked in (after the eighth clock). This allows any number of bytes to be written without page buffer delays.


**Note** If the power is lost in the middle of the write operation, only the last completed byte will be written.



#### **Read Operation**

After the falling edge of  $\overline{CS}$ , the bus master can issue a READ opcode. Following the READ command is a three-byte address containing the 18-bit address (A17-A0) of the first byte of the read operation. The upper six bits of the address are ignored. After the opcode and address are issued, the device drives out the read data on the next eight clocks. The SI input is ignored

during read data bytes. Subsequent bytes are data bytes, which are read out sequentially. Addresses are incremented internally as long as the bus master continues to issue clocks and  $\overline{\text{CS}}$  is LOW. If the last address of 3FFFFh is reached, the counter  $\underline{\text{will}}$  roll over to 00000h. Data is read MSB first. The rising edge of  $\overline{\text{CS}}$  terminates a read operation and tristates the SO pin. A read operation is shown in Figure 12.






#### **HOLD Pin Operation**

The  $\overline{\text{HOLD}}$  pin can be used to interrupt a serial operation without aborting it. If the bus master pulls the  $\overline{\text{HOLD}}$  pin LOW while SCK is LOW, the current operation will pause. Taking the  $\overline{\text{HOLD}}$  pin

HIGH while <u>SCK</u> is LOW will resume an operation. The transitions of <u>HOLD</u> must occur while SCK is LOW, but the SCK and <u>CS</u> pin can toggle during a hold state.



#### Sleep Mode

A low-power sleep mode is implemented on the FM25V20 device. The device will enter the low-power state when the SLEEP opcode B9h is clocked in and a rising edge of  $\overline{CS}$  is applied. When in sleep mode, the SCK and SI pins are ignored and SO will be HI-Z, but the device continues to monitor the  $\overline{CS}$ 

pin. On the next falling edge of  $\overline{\text{CS}}$ , the device will return to normal operation within  $t_{\text{REC}}$  time. The SO pin remains in a HI-Z state during the wakeup period. The device does not necessarily respond to an opcode within the wakeup period. To start the wakeup procedure, the controller may send a "dummy" read, for example, and wait the remaining  $t_{\text{REC}}$  time.

Enters Sleep Mode

CS

0 1 2 3 4 5 6 7

SCK

SI

1 0 1 1 1 0 0 1 VALID IN

HI-Z

Figure 14. Sleep Mode Operation

#### Note

Document Number: 001-85935 Rev. \*G

SO

<sup>2.</sup> Figure shows HOLD operation for input mode and output mode.



#### **Endurance**

The FM25H20 devices are capable of being accessed at least 10<sup>14</sup> times, reads or writes. An F-RAM memory operates with a read and restore mechanism. Therefore, an endurance cycle is applied on a row basis for each access (read or write) to the memory array. The F-RAM architecture is based on an array of rows and columns of 32K rows of 64-bits each. The entire row is internally accessed each time a byte in that row is read or written. All 8 bytes in the row are counted separately for each access in an endurance calculation. Table 7 shows endurance calculations for a 256-byte repeating loop, which includes an opcode, a starting address (3 bytes), and a sequential 256-byte data stream. This causes each byte to experience eight endurance

cycle through the loop. F-RAM read and write endurance is virtually unlimited even at a 40-MHz clock rate.

Table 6. Time to Reach Endurance Limit for Repeating 256-byte Loop

SCK Freq (MHz)	Endurance Cycles/sec	Endurance Cycles/year	Years to Reach Limit
40	153,848	$4.85 \times 10^{12}$	20.6
20	76,924	$2.43 \times 10^{12}$	41.2
10	38,462	1.21 × 10 <sup>12</sup>	82.4
5	19,231	6.06 × 10 <sup>11</sup>	164.8





# **Maximum Ratings**

Exceeding maximum ratings may shorten the useful life of the device. These user guidelines are not tested.

de l'est l'illes des galdemies die l'et tested.
Storage temperature55 °C to +125 °C
Maximum junction temperature 95 °C
Supply voltage on $V_{DD}$ relative to $V_{SS}$ 1.0 V to +4.5 V
Input voltage $-1.0$ V to +4.5 V and $V_{IN}$ < $V_{DD}$ + 1.0 V
DC voltage applied to outputs in High-Z state0.5 V to $V_{DD}$ + 0.5 V
Transient voltage (< 20 ns) on any pin to ground potential2.0 V to $V_{DD}$ + 2.0 V
Package power dissipation capability (T <sub>A</sub> = 25 °C)1.0 W

Surface mount lead soldering temperature (3 seconds)+260 °C
DC output current (1 output at a time, 1s duration) 15 mA
Electrostatic Discharge Voltage Human Body Model (JEDEC Std JESD22-A114-B) 2 kV
Charged Device Model (JEDEC Std JESD22-C101-A) 1 kV
Machine Model (JEDEC Std JESD22-A115-A)200 V
Latch-up current> 50 mA

# **Operating Range**

Range	Ambient Temperature (T <sub>A</sub> )	V <sub>DD</sub>
Industrial	-40 °C to +85 °C	2.7 V to 3.6 V

## **DC Electrical Characteristics**

Over the Operating Range

Parameter	Description	Test Conditions		Min	<b>Typ</b> <sup>[3]</sup>	Max	Unit
V <sub>DD</sub>	Power supply			2.7	3.3	3.6	V
I <sub>DD</sub>	V <sub>DD</sub> supply current	SCK toggling f <sub>SCK</sub>	=1 MHz;	-	-	1	mA
		between $V_{DD} - 0.2 \text{ V}$ and $V_{SS}$ , other inputs $V_{SS}$ or $V_{DD} - 0.2 \text{ V}$ . SO = Open	= 40 MHz;	-	-	10	mA
I <sub>SB</sub>	V <sub>DD</sub> standby current	$\overline{\text{CS}} = V_{\text{DD}}$ . All other $T_{\text{A}} =$	25 °C	-	80	150	μΑ
		inputs $V_{SS}$ or $V_{DD}$ . $T_A =$	85 °C	-	_	270	μΑ
I <sub>ZZ</sub>	Sleep mode current	$\overline{CS} = V_{DD}$ . $T_A =$	25 °C	-	3	5	μΑ
		All other inputs $V_{SS}$ or $T_A = V_{DD}$ .	85 °C	_	-	8	μА
I <sub>LI</sub>	Input leakage current	$V_{SS} \leq V_{IN} \leq V_{DD}$		-	-	±1	μΑ
I <sub>LO</sub>	Output leakage current	$V_{SS} \le V_{OUT} \le V_{DD}$		-	-	±1	μΑ
V <sub>IH</sub>	Input HIGH voltage			$0.7 \times V_{DD}$	_	V <sub>DD</sub> + 0.5	V
V <sub>IL</sub>	Input LOW voltage			- 0.4	_	0.3 × V <sub>DD</sub>	V
V <sub>OH</sub>	Output HIGH voltage	I <sub>OH</sub> = -100 μA		V <sub>DD</sub> – 0.2	_	_	V
V <sub>OL</sub>	Output LOW voltage	I <sub>OL</sub> = 1.6 mA		_	_	0.4	V

Document Number: 001-85935 Rev. \*G

Note 3. Typical values are at 25 °C,  $V_{DD}$  =  $V_{DD}$  (typ). Not 100% tested.



# **Data Retention and Endurance**

Parameter	Description	Test condition	Min	Max	Unit
$T_{DR}$	Data retention	T <sub>A</sub> = 85 °C	10	_	Years
		T <sub>A</sub> = 75 °C	38	_	
		T <sub>A</sub> = 65 °C	151	_	
$NV_C$	Endurance	Over operating temperature	10 <sup>14</sup>	_	Cycles

# Capacitance

Parameter [4]	Description	Test Conditions	Max	Unit
Co	Output pin capacitance (SO)	$T_A = 25 ^{\circ}\text{C}$ , $f = 1 \text{MHz}$ , $V_{DD} = V_{DD}(typ)$	8	pF
C <sub>I</sub>	Input pin capacitance		6	pF

# **Thermal Resistance**

Parameter	Description	Test Conditions	8-pin SOIC	8-pin TDFN	Unit
$\Theta_{JA}$	,	Test conditions follow standard test methods and procedures for measuring	112	16	°C/W
$\Theta_{\sf JC}$	Thermal resistance (junction to case)	thermal impedance, per EIA / JESD51.	37	10	°C/W

# **AC Test Conditions**

Input pulse levels	10% and 90°	% of V <sub>DD</sub>
Input rise and fall times		3 ns
Input and output timing reference leve	ls0	$.5 \times V_{DD}$
Output load capacitance		30 pF

Document Number: 001-85935 Rev. \*G

<sup>4.</sup> This parameter is characterized but not 100% tested.



# **AC Switching Characteristics**

Over the Operating Range


Parameters [5]			V <sub>DD</sub> = 2.7	V to 3.6 V	
Cypress Parameter	Alt. Parameter	Description	Min	Max	Unit
f <sub>SCK</sub>	_	SCK clock frequency	0	40	MHz
t <sub>CH</sub>	_	Clock HIGH time	11	-	ns
t <sub>CL</sub>	_	Clock LOW time	11	_	ns
t <sub>CSU</sub>	t <sub>CSS</sub>	Chip select setup	10	_	ns
t <sub>CSH</sub>	t <sub>CSH</sub>	Chip select hold	10	-	ns
t <sub>OD</sub> <sup>[6, 7]</sup>	t <sub>HZCS</sub>	Output disable time	_	12	ns
t <sub>ODV</sub>	t <sub>CO</sub>	Output data valid time	-	9	ns
t <sub>OH</sub>	_	Output hold time	0	-	ns
t <sub>D</sub>	_	Deselect time	40	-	ns
t <sub>R</sub> <sup>[8, 9]</sup>	_	Data in rise time	-	50	ns
t <sub>F</sub> <sup>[8, 9]</sup>	_	Data in fall time	-	50	ns
t <sub>SU</sub>	t <sub>SD</sub>	Data setup time	5	-	ns
t <sub>H</sub>	t <sub>HD</sub>	Data hold time	5	_	ns
t <sub>HS</sub>	t <sub>SH</sub>	HOLD setup time	10	_	ns
t <sub>HH</sub>	t <sub>HH</sub>	HOLD hold time	10	_	ns
t <sub>HZ</sub> [6, 7]	t <sub>HHZ</sub>	HOLD LOW to HI-Z	_	20	ns
t <sub>LZ</sub> <sup>[7]</sup>	t <sub>HLZ</sub>	HOLD HIGH to data active	-	20	ns

#### Notes

- 5. Test conditions assume a signal transition time of 3 ns or less, timing reference levels of 0.5 x V<sub>DD</sub>, input pulse levels of 10% to 90% of V<sub>DD</sub>, and output loading of the specified I<sub>OL</sub>/I<sub>OH</sub> and 30 pF load capacitance shown in AC Test Conditions on page 13.
- 6. t<sub>OD</sub> and t<sub>HZ</sub> are specified with a load capacitance of 5 pF. Transition is measured when the outputs enter a high impedance state
- 7. This parameter is characterized but not 100% tested.
- 8. Rise and fall times measured between 10% and 90% of waveform.
- 9. These parameters are guaranteed by design and are not tested.



Figure 15. Synchronous Data Timing (Mode 0)





# **Power Cycle Timing**

Over the Operating Range

Parameter	Description	Min	Max	Unit
t <sub>PU</sub>	Power-up V <sub>DD</sub> (min) to first access ( <del>CS</del> LOW)	1	_	ms
t <sub>PD</sub>	Last access (CS HIGH) to power-down (V <sub>DD</sub> (min))	0	_	μs
t <sub>VR</sub> <sup>[10]</sup>	V <sub>DD</sub> power-up ramp rate	50	_	µs/V
t <sub>VF</sub> <sup>[10]</sup>	V <sub>DD</sub> power-down ramp rate	100	_	µs/V
t <sub>REC</sub> [11]	Recovery time from sleep mode	_	450	μs

Figure 17. Power Cycle Timing  $v_{DD(\underline{min})}$ VDD(min)  $V_{\text{DD}}$  $t_{PU}$  $\overline{\text{cs}}$ 

#### Notes

<sup>10.</sup> Slope measured at any point on the V<sub>DD</sub> waveform.
11. Guaranteed by design. Refer to Figure 14 for sleep mode recovery timing.




# **Ordering Information**

Ordering Code	Package Diagram	Package Type	Operating Range
FM25H20-G	001-85261	8-pin SOIC	Industrial
FM25H20-GTR	001-85261	8-pin SOIC	
FM25H20-DG	001-85579	8-pin TDFN	
FM25H20-DGTR	001-85579	8-pin TDFN	

All these parts are Pb-free. Contact your local Cypress sales representative for availability of these parts.


#### **Ordering Code Definitions**





# **Package Diagrams**


Figure 18. 8-pin SOIC (208 Mils) Package Outline, 001-85261





# Package Diagrams (continued)

Figure 19. 8-pin DFN (5 mm × 6 mm × 0.75 mm) Package Outline, 001-85579



001-85579 \*A



# **Acronyms**

Acronym	Description					
СРНА	Clock Phase					
CPOL	Clock Polarity					
EEPROM	Electrically Erasable Programmable Read-Only Memory					
EIA	Electronic Industries Alliance					
F-RAM	Ferroelectric Random Access Memory					
I/O	Input/Output					
JEDEC	Joint Electron Devices Engineering Council					
JESD	JEDEC Standards					
LSB	Least Significant Bit					
MSB	Most Significant Bit					
RoHS	Restriction of Hazardous Substances					
SPI	Serial Peripheral Interface					
SOIC	Small Outline Integrated Circuit					
TDFN	Thin Dual Flat No-lead					

# **Document Conventions**

## **Units of Measure**

Symbol	Unit of Measure
°C	degree Celsius
Hz	hertz
kHz	kilohertz
kΩ	kilohm
Mbit	megabit
MHz	megahertz
μΑ	microampere
μF	microfarad
μS	microsecond
mA	mil <mark>liamp</mark> ere
ms	millisecond
ns	nanosecond
Ω	ohm
%	percent
pF	picofarad
V	volt
W	watt



# **Document History Page**

Document Document	Title: FM25H Number: 001	120, 2-Mbit ( 1-85935	256 K × 8) Ser	ial (SPI) F-RAM
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	3902952	GVCH	02/25/13	New spec
*A	3924836	GVCH	03/07/13	Move datasheet to external web
*B	3994285	GVCH	05/14/2013	Added Appendix A - Errata for FM25H20
*C	4045438	GVCH	06/30/2013	All errata items are fixed and the errata is removed.
*D	4226252	GVCH	01/24/2014	Converted to Cypress standard format  Updated Pinouts
				- Updated Figure 2 (Added EXPOSED PAD details)
				Updated Pin Definitions - Added EXPOSED PAD details.
				Updated Maximum Ratings table - Removed Moisture Sensitivity Level (MSL) - Added junction temperature and latch up current
				Updated Data Retention and Endurance table - Added data retention value at 65 °C and 75 °C temperature
				Added Thermal Resistance table
				Updated Package Diagrams: Removed Package Marking Scheme (top mark). Updated Figure 19.
				Removed Ramtron revision history.
				Completing Sunset Review.
				Added watermark as "Not Recommended for New Designs".
*E	4462384	GVCH	07/31/2014	Updated Package Diagrams: spec 001-85579 – Changed revision from ** to *A.
*F	4574376	GVCH	11/19/2014	Added related documentation hyperlink in page 1.
*G	4785411	GVCH	06/03/2015	Obsolete document.



# Sales, Solutions, and Legal Information

#### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

#### **Products**

Automotive

Clocks & Buffers

Interface

**Lighting & Power Control** 

Memory PSoC

**Touch Sensing** 

**USB Controllers** 

Wireless/RF

cypress.com/go/automotive cypress.com/go/clocks cypress.com/go/interface cypress.com/go/powerpsoc cypress.com/go/plc cypress.com/go/memory cypress.com/go/psoc cypress.com/go/touch cypress.com/go/USB

#### PSoC® Solutions

psoc.cypress.com/solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP

#### **Cypress Developer Community**

Community | Forums | Blogs | Video | Training

#### **Technical Support**



© Cypress Semiconductor Corporation, 2013-2015. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.