

Reverse-Conducting IGBT with monolithic body diode

Features

- $V_{CE} = 650\text{ V}$
- $I_C = 50\text{ A}$
- Powerful monolithic diode optimized for ZCS applications
- High ruggedness, temperature stable behavior
- Very low V_{CEsat} and low E_{off}
- Easy paralleling capability due to positive temperature coefficient in V_{CEsat}
- Low EMI
- Low electrical parameters depending (dependence) on temperature
- Qualified according to JESD-022 for target applications
- Pb-free lead plating; RoHS compliant
- Complete product spectrum and PSpice Models: <http://www.infineon.com/igbt/>

Potential applications

- Welding
- PFC
- ZCS - converters



Lead-Free



Green




Halogen-Free



RoHS

Description



Type	Package	Marking
IKW50N65WR5	PG-TO247-3	K50EWR5

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Table of contents	2
1	Package	3
2	IGBT	3
3	Diode	5
4	Characteristics diagrams	7
5	Package outlines	13
6	Testing conditions	14
	Revision history	15
	Disclaimer	16

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Internal emitter inductance measured 5 mm (0.197 in.) from case	L_E			13.0		nH
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature		wave soldering 1.6 mm (0.063 in.) from case for 10 s			260	°C
Mounting torque	M	M3 screw Maximum of mounting process: 3			0.6	Nm
Thermal resistance, junction-ambient	$R_{th(j-a)}$				40	K/W

2 IGBT

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CE}	$T_{vj} \geq 25\text{ °C}$		650	V
DC collector current, limited by T_{vjmax}	I_C	limited by bondwire	$T_c = 25\text{ °C}$	80	A
			$T_c = 130\text{ °C}$	50	
Pulsed collector current, t_p limited by T_{vjmax}	I_{Cpulse}			150	A
Turn-off safe operating area		$V_{CE} \leq 650\text{ V}, T_{vj} \leq 175\text{ °C}$		150	A
Gate-emitter voltage	V_{GE}			± 20	V
Transient gate-emitter voltage	V_{GE}	$t_p \leq 10\text{ }\mu\text{s}, D < 0.01$		± 30	V
Power dissipation	P_{tot}		$T_c = 25\text{ °C}$	282	W
			$T_c = 130\text{ °C}$	141	

Table 3 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter breakdown voltage	V_{BRCES}	$I_C = 0.2\text{ mA}, V_{GE} = 0\text{ V}$	650			V
Collector-emitter saturation voltage	V_{CEsat}	$I_C = 50\text{ A}, V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	1.4	1.8	V
			$T_{vj} = 175\text{ °C}$	1.65		
Gate-emitter threshold voltage	V_{GETh}	$I_C = 0.5\text{ mA}, V_{CE} = V_{GE}$	3.2	4	4.8	V

(table continues...)
Datasheet

Table 3 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Zero gate-voltage collector current	I_{CES}	$V_{CE} = 650 \text{ V}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$			40	μA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0 \text{ V}$, $V_{GE} = 20 \text{ V}$				100	nA
Transconductance	g_{fs}	$I_C = 50 \text{ A}$, $V_{CE} = 20 \text{ V}$			65		S
Input capacitance	C_{ies}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1000 \text{ kHz}$			6140		pF
Output capacitance	C_{oes}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1000 \text{ kHz}$			55		pF
Reverse transfer capacitance	C_{res}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1000 \text{ kHz}$			23		pF
Gate charge	Q_G	$I_C = 50 \text{ A}$, $V_{GE} = 15 \text{ V}$, $V_{CC} = 520 \text{ V}$			230		nC
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		45		ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		43		
Rise time (inductive load)	t_r	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		17		ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		19		
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		417		ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		496		
Fall time (inductive load)	t_f	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		16		ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		11		
Turn-on energy	E_{on}	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		0.84		mJ
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		1.04		
Turn-off energy	E_{off}	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		0.22		mJ
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		0.32		
Total switching energy	E_{ts}	$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{Gon} = 16 \text{ }\Omega$, $R_{Goff} = 16 \text{ }\Omega$, $L_\sigma = 45 \text{ nH}$, $C_\sigma = 32 \text{ pF}$	$T_{vj} = 25 \text{ °C}$, $I_C = 25 \text{ A}$		1.06		mJ
			$T_{vj} = 175 \text{ °C}$, $I_C = 25 \text{ A}$		1.36		

(table continues...)

Table 3 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
IGBT thermal resistance, junction to case	$R_{th(j-c)}$				0.53	K/W
Operating junction temperature	T_{vj}		-40		175	°C

Note: Electrical Characteristic, at $T_{vj} = 25^{\circ}\text{C}$, unless otherwise specified.

3 Diode

Table 4 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} \geq 25^{\circ}\text{C}$	650	V
Diode forward current, limited by T_{vjmax}	I_F	limited by bondwire	$T_c = 25^{\circ}\text{C}$	A
			$T_c = 100^{\circ}\text{C}$	
Diode pulsed current, t_p limited by T_{vjmax}	I_{Fpulse}		150	A

Table 5 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Diode forward voltage	V_F	$I_F = 25\text{ A}$	$T_{vj} = 25^{\circ}\text{C}$	1.4	1.9	V
			$T_{vj} = 175^{\circ}\text{C}$	1.5		
Diode reverse recovery time	t_{rr}	$V_R = 400\text{ V}$	$T_{vj} = 25^{\circ}\text{C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A}/\mu\text{s}$	110		ns
			$T_{vj} = 175^{\circ}\text{C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A}/\mu\text{s}$	145		
Diode reverse recovery charge	Q_{rr}	$V_R = 400\text{ V}$	$T_{vj} = 25^{\circ}\text{C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A}/\mu\text{s}$	1.8		μC
			$T_{vj} = 175^{\circ}\text{C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A}/\mu\text{s}$	3.5		

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Diode peak reverse recovery current	I_{rrm}	$V_R = 400\text{ V}$	$T_{vj} = 25\text{ °C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A/}\mu\text{s}$		29		A
			$T_{vj} = 175\text{ °C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A/}\mu\text{s}$		39		
Diode peak rate of fall of reverse recovery current	di_{rr}/dt	$V_R = 400\text{ V}$	$T_{vj} = 25\text{ °C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A/}\mu\text{s}$		600		A/ μs
			$T_{vj} = 175\text{ °C}$, $I_F = 25\text{ A}$, $-di_F/dt = 900\text{ A/}\mu\text{s}$		1200		
Diode thermal resistance, junction to case	$R_{th(j-c)}$					2.29	K/W
Operating junction temperature	T_{vj}			-40		175	°C


Note: For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.

4 Characteristics diagrams

Reverse bias safe operating area

$$I_C = f(V_{CE})$$


$$T_{vj} \leq 175\text{ °C}, V_{GE} = 15\text{ V}, T_c = 25\text{ °C}$$



Power dissipation as a function of case temperature

$$P_{tot} = f(T_c)$$


$$T_{vj} \leq 175\text{ °C}$$



Collector current as a function of case temperature

$$I_C = f(T_c)$$


$$T_{vj} \leq 175\text{ °C}, V_{GE} \geq 15\text{ V}$$



Typical output characteristic


$$I_C = f(V_{CE})$$

$$T_{vj} = 25\text{ °C}$$




Typical output characteristic

$I_C = f(V_{CE})$
 $T_{vj} = 175^\circ\text{C}$




Typical transfer characteristic

$I_C = f(V_{GE})$
 $V_{CE} = 20\text{ V}$




Typical collector-emitter saturation voltage as a function of junction temperature

$V_{CEsat} = f(T_{vj})$
 $V_{GE} = 15\text{ V}$



Typical switching times as a function of collector current


$t = f(I_C)$
 $V_{CC} = 400\text{ V}, T_{vj} = 175^\circ\text{C}, V_{GE} = 0/15\text{ V}, R_G = 16\ \Omega$



Typical switching times as a function of gate resistor

$$t = f(R_G)$$


$I_C = 50 \text{ A}$, $V_{CC} = 400 \text{ V}$, $T_{vj} = 175 \text{ }^\circ\text{C}$, $V_{GE} = 0/15 \text{ V}$



Typical switching times as a function of junction temperature

$$t = f(T_{vj})$$


$I_C = 50 \text{ A}$, $V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 16 \text{ } \Omega$



Gate-emitter threshold voltage as a function of junction temperature

$$V_{GEth} = f(T_{vj})$$


$I_C = 0.5 \text{ mA}$



Typical switching energy losses as a function of collector current

$$E = f(I_C)$$

$V_{CC} = 400 \text{ V}$, $T_{vj} = 175 \text{ }^\circ\text{C}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 16 \text{ } \Omega$




4 Characteristics diagrams

Typical switching energy losses as a function of gate resistor

$$E = f(R_G)$$


$I_C = 50 \text{ A}$, $V_{CC} = 400 \text{ V}$, $T_{vj} = 175 \text{ }^\circ\text{C}$, $V_{GE} = 0/15 \text{ V}$



Typical switching energy losses as a function of junction temperature

$$E = f(T_{vj})$$


$V_{CC} = 400 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 16 \text{ } \Omega$, $I_C = 50 \text{ A}$



Typical gate charge

$$V_{GE} = f(Q_G)$$


$I_C = 50 \text{ A}$



Typical capacitance as a function of collector-emitter voltage

$$C = f(V_{CE})$$


$f = 1000 \text{ kHz}$, $V_{GE} = 0 \text{ V}$



4 Characteristics diagrams


IGBT transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$
 $D = t_p/T$




Diode transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$
 $D = t_p/T$




Typical reverse recovery time as a function of diode current slope

$t_{rr} = f(di_F/dt)$
 $V_R = 400\text{ V}, I_F = 25\text{ A}$



Typical reverse recovery charge as a function of diode current slope


$Q_{rr} = f(di_F/dt)$
 $V_R = 400\text{ V}, I_F = 25\text{ A}$



Typical reverse recovery current as a function of diode current slope

$$I_{rr} = f(di_F/dt)$$


$V_R = 400 \text{ V}$, $I_F = 25 \text{ A}$



Typical diode peak rate of fall of reverse recovery current as a function of diode current slope


$$di_{rr}/dt = f(di_F/dt)$$

$V_R = 400 \text{ V}$, $I_F = 25 \text{ A}$




Typical diode forward current as a function of forward voltage

$$I_F = f(V_F)$$



Typical diode forward voltage as a function of junction temperature

$$V_F = f(T_{vj})$$



5 Package outlines




Figure 1

6 Testing conditions




Figure A. Definition of switching times




Figure B. Definition of switching losses




Figure C. Definition of diode switching characteristics




Figure D. Thermal equivalent circuit




Figure E. **Dynamic test circuit**
Parasitic inductance L_σ ,
parasitic capacitor C_σ ,
relief capacitor C_r ,
(only for ZVT switching)

Revision history

Document revision	Date of release	Description of changes
V1.1	2014-12-05	Preliminary data sheet
V1.2	2015-03-27	New dynamic parameters and graphs
V1.3	2015-05-13	
V2.1	2015-12-10	Final data sheet
n/a	2020-11-30	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.10	2022-03-08	Added transient gate-emitter voltage
1.20	2022-05-06	Transient gate-emitter voltage V_{GE} added in table “Maximum rated values” of IGBT “Forward bias safe operating area” diagram renamed to “Reverse bias safe operating area”

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-05-06

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2022 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAK880-006

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.