# TLE8209-2SA

SPI Programmable H-Bridge

**Automotive Power** 





#### **Table of Contents**

# **Table of Contents**

I	Overview	. 3
2.1 2.2 2.3	Pin Configuration Pin Assignment Pin Definitions and Functions Terms	. 4 . 4
3	Block Diagram	. 6
<b>1</b> 1.1 1.2 1.3	General Product Characteristics Absolute Maximum Ratings Operating Range Thermal Resistance	. 7 . 8
5.1 5.2 5.3 5.4	Power Supply  Basic Supply Characteristics  VDD Monitoring  VDDIO - Digital Output Supply and Diagnostic Mode Selection  Electrical Characteristics Power Supply and V <sub>DD</sub> -Monitoring	. 9 . 9 10 11
3	Logic Inputs and Outputs	12
7 7.1 7.2 7.3	Power Stages Parallel or SPI Control H-Bridge or Single Switch Usage Electrical Characteristics Power Stages	14 14
3.1 3.2 3.3 3.4 3.5 3.6 3.7 3.8 3.9 3.10	Protection and Monitoring Diagnosis in Status Flag Mode Current Limitation Temperature Dependent Current Reduction Short Circuit to Ground Short Circuit to Battery Short Circuit across the Load Overtemperature Undervoltage Shut-Down Open Load Diagnosis Electrical Characteristics	18 18 19 19 20 20 20 20 20 22
9.1 9.2 9.3	SPI Interface General SPI Characteristics SPI Communication Electrical Characteristics SPI	24 25
10	Application Information	34
11	Package Outlines TLE8209-2SA	36
12	Revision History	37



#### **SPI Programmable H-Bridge**

**TLE8209-2SA** 





#### 1 Overview

#### **Features**

- Programmable current limitation from 1.5 to 8.6 A typ.
- Full path  $R_{\rm DSon}$  of 240 m $\Omega$  (typ. at Tj=25°C)
- Operating battery supply voltage 4.5 V to 28 V
- Operating logic supply voltage 4.4 to 5.25 V
- Low standby current (8 μA typ.)
- Logic inputs TTL/CMOS-compatible
- All I/O pins overvoltage tolerant up to 18 V
- · Enable and disable input
- Short circuit and overtemperature protection
- V<sub>S</sub> undervoltage shutdown
- V<sub>DD</sub> over- and undervoltage monitoring
- Open load detection in off condition
- Temperature dependent current reduction
- Extensive diagnosis capabilities via SPI interface
- Status Flag for basic diagnosis without SPI
- · Configurable as H-bridge or two independent half bridges
- Control of power stages by parallel inputs or via SPI
- Output switching frequency up to 11 kHz
- Slewrate programmable through SPI
- Excellent EMC performance
- · AEC qualified
- Green product (RoHS compliant)

# Infineon PG-DSO-20

PG-DSO-20-65

#### **Functional Description**

The TLE8209-2SA is a SPI programmable H-bridge, designed for the control of DC motors in safety critical automotive applications. It features four selectable current ranges, two selectable slew rate settings and extensive diagnosis via SPI. The device monitors the digital supply voltage  $V_{\rm DD}$  and shuts down the output stages in case of  $V_{\rm DD}$  over- or undervoltage, thus providing a safe switch off path in case of malfunction of the digital control circuitry.

In order to reduce power dissipation in extreme thermal conditions the current limitation threshold is reduced linearly for junction temperatures over 165°C. A thermal warning bit is set in the SPI.

The two half bridges can also be used independently to drive two separate loads like solenoids or unidirectional DC motors.

Туре	Package	Body Width	Marking
TLE8209-2SA	PG-DSO-20-65	430 mil	TLE8209-2SA

Data Sheet 3 Rev. 1.2, 2012-12-20



**Pin Configuration** 

# 2 Pin Configuration

# 2.1 Pin Assignment




Figure 1 Pinout TLE8209-2SA

#### 2.2 Pin Definitions and Functions

Pin	Symbol	Function in SPI Mode	Function in Status Flag Mode
1	GND	Ground	Ground
2	SO	SPI Serial Data Out	no function - connect to GND
3	VDDIO	Supply Voltage for Logic Output Buffer	Switches to SF-mode if connected to GND
4	SS/SF	Slave Select (low active)	Status Flag (low active)
5	СР	Pin for external Charge Pump Capacitor	Pin for external Charge Pump Capacitor
6	VS	Battery Supply Voltage, has to be connected to pin 15	Battery Supply Voltage, has to be connected to pin 15
7	IN1	Input 1	Input 1
8	OUT1	Output 1	Output 1
9	DIS	Disable	Disable
10	GND	Ground	Ground
11	GND	Ground	Ground
12	ABE	Bidirectional Enable Pin	Bidirectional Enable Pin
13	OUT2	Output 2	Output 2
14	IN2	Input 2	Input 2
15	VS	Input battery supply voltage, has to be connected to pin 6	Input battery supply voltage, has to be connected to pin 6
16	SI	SPI Serial Data Input	no function - connect to GND



#### **Pin Configuration**

Pin	Symbol	Function in SPI Mode	Function in Status Flag Mode
17	SCK	SPI Clock	no function - connect to GND
18	VDD	$V_{ m DD}$ supply	$V_{ m DD}$ supply
19	GNDABE	Sense ground for $V_{\mathrm{DD}}$ monitoring	Sense ground for $V_{\mathrm{DD}}$ monitoring
20	GND	Ground	Ground
21	GND	Heatslug - connect to GND	Heatslug - connect to GND

#### 2.3 Terms




Figure 2 Terms TLE8209-2SA



**Block Diagram** 

# 3 Block Diagram




Figure 3 Block Diagram TLE8209-2SA



**General Product Characteristics** 

#### 4 General Product Characteristics

#### 4.1 Absolute Maximum Ratings

#### Absolute Maximum Ratings 1)

 $T_{\rm j}$  = -40 ·C to 150 ·C; all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit	Values	Unit	<b>Test Conditions / Comment</b>	
			Min.	Max.			
4.1.1	Junction temperature	$T_{i}$	-40	150	°C	_	
		,	150	175		100h cumulative	
4.1.2	Storage temperature	$T_{s}$	-55	150	°C	_	
4.1.3	Ambient temperature	$T_{a}$	-40	125	°C	_	
4.1.4	Battery supply voltage	$V_{S}$	-0.5	40	V	Static destruction proof	
			-2	40	V	Dynamic destruction proof $t < 0.5$ s (single pulse, $T_{jstart} < 85$ °C)	
4.1.5	Logic supply voltage	$V_{DD}$	-0.5	18	V	_	
4.1.6	Supply for logic out	$V_{DDIO}$	-0.5	18	V	_	
4.1.7	Voltage at logic pins  ABE, IN1, IN2, DIS, SCK, SS/SF, SI	$V_{IN}$	-0.5	18	V	-	
4.1.8	Voltage at SO	$V_{SO}$	-0.5	<i>V</i> <sub>DDIO</sub> +0.3	V	-	
4.1.9	Voltage at CP	$V_{CP}$	V <sub>S</sub> -0.3	V <sub>S</sub> +5.0	V	0V < V <sub>S</sub> < 40V	
4.1.10	Voltage at GNDABE	$V_{GNDABE}$	$V_{GND}$ -0.3	$V_{\rm GND}$ +0.3	V		
ESD Su	sceptibility	+	+	+			
4.1.11	ESD Resistivity to GND	$V_{ESD}$	-2	2	kV	HBM <sup>2)</sup>	
4.1.12			-8	8	kV	HBM <sup>2)</sup> , Pins OUT1 and OUT2	
4.1.13			-500	500	V	CDM <sup>3)</sup>	
4.1.14			-750	750	V	CDM <sup>3)</sup> , Pins 1, 10, 11, 20	

<sup>1)</sup> Not subject to production test, specified by design.

Note: Stresses above the ones listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Note: Integrated protection functions are designed to prevent IC destruction under fault conditions described in the data sheet. Fault conditions are considered as "outside" normal operating range. Protection functions are not designed for continuous repetitive operation.

<sup>2)</sup> ESD susceptibility HBM according to EIA/JESD22-A114-B (1.5k $\Omega$ , 100pF)

<sup>3)</sup> ESD susceptibility, Charged Device Model "CDM" EIA/JESD22-C101



#### **General Product Characteristics**

# 4.2 Operating Range

Pos.	Parameter	Symbol	Limit Values		Limit Values		Unit	Remark
			Min.	Max.				
4.2.1	$V_{\rm S}$ supply voltage range	$V_{S}$	4.5	28	V	-		
4.2.2	$V_{\mathrm{DD}}$ supply voltage	$V_{DD}$	4.4	5.25	V	-		
4.2.3	$V_{\mathrm{DDIO}}$ supply voltage	$V_{DDIO}$	0	5.5	V	-		
4.2.4	PWM frequency	f	_	11	kHz	-		
4.2.5	Junction temperature	$T_{J}$	-40	150	°C	_		

Note: Within the operating range the IC operates as described in the circuit description. The electrical characteristics are specified within the conditions given in the related electrical characteristics table.

#### 4.3 Thermal Resistance

Pos.	Parameter	Symbol	Limit Values			Unit	Remark
			Min.	Тур.	Max.		
4.3.6	Junction to Case <sup>1)</sup>	$R_{thJC}$	_	_	1.6	K/W	-
4.3.7	Junction to Ambient <sup>1)</sup>	$R_{thJA}$	_	17	_	K/W	2)

<sup>1)</sup> Not subject to production test, specified by design.

Data Sheet 8 Rev. 1.2, 2012-12-20

<sup>2)</sup> Simulation according to Jedec JESD51-2,-5,-7; natural convection; FR4 2s2p board 76.2 x 114.3 x 1.5 mm (2 x  $70\mu$ m Cu, 2 x  $35\mu$ m Cu)



**Power Supply** 

# 5 Power Supply

#### 5.1 Basic Supply Characteristics

The TLE8209-2SA has three different supply pins: VDD, VS and VDDIO. VDD is used to supply the internal logic circuitry. VS connects to battery voltage and supplies the output stages. The voltage at pin VDDIO defines the high level output voltage at the pin SO of the SPI interface. VDDIO is also used as a mode select pin. If VDDIO is connected to ground, the device is set to status flag mode (SPI inactive).

On power up the device will enter a functional state when  $V_{\rm DD}$  rises above the functional reset threshold  $V_{\rm DD\_RES}$ . In this state all output stages are inactive and internal registers are cleared. When  $V_{\rm DD}$  rises further above the power on reset threshold  $V_{\rm DD\_POR}$  the device starts operation with a delay time of  $t_{\rm POR}$ .

#### 5.2 VDD Monitoring

The logic supply voltage level at the pin VDD is monitored. If the voltage at pin  $V_{\rm DD}$  is out of the permissible range of  $V_{\rm DD\_L}$  ...  $V_{\rm DD\_H}$  the power stages of TLE8209-2SA are switched off and pin ABE is pulled to ground. To suppress glitches in the  $V_{\rm DD}$  monitoring, a glitch filter is implemented.  $V_{\rm DD}$  is measured with reference to pin GNDABE. The state of VDD monitoring is stored in STATCON\_REG and can be read out via SPI.

The output stages can also be turned off by pulling the ABE pin to ground externally.

In case of VDD failure, the output stages are switched off, even if the pin  $\overline{ABE}$  should be connected to a high level signal because of external short circuit to VDD or battery voltage (up to 18V). OUT1 and OUT2 cannot be switched on in over- or undervoltage condition, switching off is always possible. A power on reset ( $V_{DD} < V_{DD\_POR}$ ) switches off all stages without delay.

Control of VDD-monitoring is possible in SPI mode only. Detailed information (differentiation of over and undervoltage detection) is only possible by SPI interface.

#### Behavior of VDD monitoring in SF mode:

- monitoring is present with the specified values for over- and undervoltage
- any test of over- and undervoltage threshold is not possible
- the latch for overvoltage is disabled

#### VDD Undervoltage

If the VDD voltage is lower than the supply voltage supervisory lower threshold ( $V_{\rm DD\_THL}$ ), output stages are shut off after a filtering time ( $t_{\rm FIL\_OFF}$ ) and the bi-directional pin  $\overline{\rm ABE}$  is pulled low. At the transition from undervoltage to normal voltage the signal at pin  $\overline{\rm ABE}$  goes high and the output stages will return to normal operation after a filtering time ( $t_{\rm FIL\_ON}$ ) has expired. For output control via SPI the bits MUX and SINx in the config register have to be reprogrammed. New failures are not stored to diagnostic registers during undervoltage, register content remains valid, writing new information to configuration registers is possible as far as they are not reset by  $\overline{\rm ABE}$ . If VDD falls below the power-on-reset supply voltage ( $V_{\rm DD\_POR}$ ) all stages are shut off and  $\overline{\rm ABE}$  is switched active low. When VDD is rising above the power-on-reset supply voltage threshold ( $V_{\rm DD\_POR}$ ) a power-on-reset is generated ( $t_{\rm POR}$ ), setting all registers to its default state.

#### VDD Overvoltage

If the VDD voltage is higher than the supply voltage supervisory upper threshold ( $V_{\rm DD\_THH}$ ), all output stages are shut off after a filtering time ( $t_{\rm FIL\_OFF}$ ) and the bi-directional pin ABE is pulled low. The behavior of the ABE level and output stages on the return of VDD from overvoltage to the correct range is configured in STATCON\_REG, bit CONFIG0)

CONFIG0='1': ABE is latched and outputs remain off after overvoltage. Return to normal operation is only possible with power-on reset or by changing this bit via SPI.

Data Sheet 9 Rev. 1.2, 2012-12-20



**Power Supply** 

CONFIG0='0': ABE is inactive after VDD returned to normal operating voltage and filtering time has expired.

At the transition from overvoltage to normal condition, the output stages will return to normal operation. For output control via SPI the bits MUX and SINx in the config register have to be re-programmed. New failures are not stored to diagnostic registers during overvoltage, register content remains valid, writing new information to configure registers is possible as far as they are not reset by  $\overline{ABE}$ .

#### **VDD Monitoring Test Mode**

Testing of VDD monitoring is possible in SPI mode only. The latch function for over voltage at VDD has to be switched of (CONFIG0=0 in STATCON REG)

#### Testing upper threshold:

By writing 00xxxxxxb into STATCON\_REG, the overvoltage threshold is reduced to VDD\_TEST\_H. STATCON\_REG bit 2 and 0 have to be LOW then. After writing 1xxxxxxxxb to STATCON\_REG, bit 2 and 0 in STATCON\_REG must be HIGH again

#### **Testing lower threshold:**

By writing 01xxxxxxb into STATCON\_REG, the undervoltage threshold is increased to VDD\_TEST\_L. STATCON\_REG bit 2 and 1 have to be LOW then. After writing 1xxxxxxxxb to STATCON\_REG, bit 2 and 1 in STATCON REG must be HIGH again.

#### 5.3 VDDIO - Digital Output Supply and Diagnostic Mode Selection

The voltage at  $V_{\rm DDIO}$  is used to supply the output buffer at the SO pin (serial output of SPI-interface). The VDDIO pin is also used to select SPI- or in status flag (SF) diagnostic mode. As soon as  $V_{\rm DDIO}$  is lower than  $V_{\rm DDIO\_L}$ , the device is put into status flag mode.




Figure 4  $V_{\rm DDIO}$  and SO-Pin



**Power Supply** 

# 5.4 Electrical Characteristics Power Supply and V<sub>DD</sub>-Monitoring

# Electrical Characteristics: Power Supply and $\mathbf{V}_{\mathrm{DD}}\text{-}\mathbf{Monitoring}$

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	<b>Test Conditions</b>
			Min.	Тур.	Max.		
Supply							
5.4.1	Supply Current	$I_{ m VS}$	_	8	20	μΑ	$I_{\text{OUT}} = 0 \text{ A, V}_{\text{DD}} = 0 \text{V,}$ $V_{\text{S}} < 18 \text{ V, T}_{\text{j}} < 125 ^{\circ}\text{C}$
			_	2.1	4	mA	bridge disabled, $I_{\rm OUT}$ = 0 A, 5 V < $V_{\rm S}$ < 18 V
			_	2.5	5	mA	$f$ = 2 kHz, $I_{\rm OUT}$ = 0 A, 5 V < $V_{\rm S}$ < 18 V
			_	4	9	mA	$f = \text{10 kHz}, I_{\text{OUT}} = \text{0 A}, \\ \text{5 V} < V_{\text{S}} < \text{18 V}$
			_	4.8	13	mA	$f = \text{10 kHz}, I_{\text{OUT}} = \text{0 A}, \\ \text{5 V} < V_{\text{S}} < \text{28 V}$
5.4.2	Functional Reset Threshold	$V_{\mathrm{DD\_RES}}$	_	1.4	2.5	V	-
5.4.3	Power On Reset Threshold	$V_{DD\_POR}$	3.5	3.75	4.0	V	_
5.4.4	Power On Reset Delay Time	$t_{POR}$	-	0.22	0.5	ms	$V_{\rm DD}$ = on> output stage active, no load
5.4.5	VDD Input current	$I_{DD}$	_	7	9	mA	4.5V < V <sub>DD</sub> < 5.5V
5.4.6	VDDIO Input current	$I_{DDIO}$	-	30	100	μA	SPI-mode no load at SO no SPI communication
5.4.7	SF-mode Threshold	$V_{DDIO\_L}$	_	_	1.0	V	_
5.4.8	SPI-mode Threshold	$V_{DDIO_H}$	2.0	_	_	V	_
5.4.9	Mode selection hysteresis	V <sub>DDIO_HYS</sub>	0.2	0.5	1.0	V	_
$\overline{V_{DD} ext{-}Mo}$	nitoring		<u> </u>	<u> </u>		<u> </u>	
5.4.10	Overvoltage threshold	$V_{ m DD\_THH}$	5.25	5.4	5.5	V	Voltage referred to
5.4.11	Undervoltage threshold	$V_{DD\_THL}$	4.2	4.3	4.4	V	GNDABE
5.4.12	Test mode reduced Overvoltage threshold	V <sub>DD_TEST_H</sub>	4.2	4.3	4.4	V	
5.4.13	Test mode increased Undervoltage threshold	$V_{ m DD\_TEST\_L}$	5.25	5.4	5.5	V	
5.4.14	Filter time for glitch suppression	$t_{FIL}$	60	100	135	μS	_
5.4.15	Maximum Slew Rate on VDD <sup>1)</sup>	$V_{ m DD\_slew}$	-	-	0.5	V/µs	-
-			•	•	-		

<sup>1)</sup> Not subject to production test; specified by design



**Logic Inputs and Outputs** 

# 6 Logic Inputs and Outputs

The threshold specifications for the logic inputs are compatible to both 5 and 3.3 V standard CMOS microcontroller ports. All inputs (except  $\overline{ABE}$ ) feature internal pull-up current sources. The logic output SO is supplied by  $V_{\rm DDIO}$ .  $V_{\rm DDIO}$  can be supplied with either 5 or 3.3 V, so the output thresholds of SO can be configured to the required I/O voltage.

#### **Electrical Characteristics: Control Inputs**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V;  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	Test Conditions
			Min.	Тур.	Max.		
N1, IN2					-		
6.0.1	Low level	$V_{INx\_L}$	-0.3	_	1.0	V	_
6.0.2	High level	$V_{INx\_H}$	2.0	_	V <sub>DD</sub> +0.3	٧	_
6.0.3	Hysteresis	$V_{INx\_HYS}$	0.2	_	1.0	٧	_
6.0.4	Input Current (Pull Up)	$I_{INx}$	-30	-20	-10	μΑ	$0 \text{ V} < V_{\text{INx}} < 2.1 \text{ V}$
6.0.5			0	2	5	μΑ	V <sub>INx</sub> > 3.0 V
6.0.6	Input Capacity <sup>1)</sup>	C <sub>INx</sub>	_	_	20	pF	2)
DIS						1-	
3.0.7	Low level	$V_{DIS\_L}$	-0.3	_	1.0	٧	_
8.0.8	High level	$V_{DIS\_H}$	2.0	_	V <sub>DD</sub> +0.3	V	_
5.0.9	Hysteresis	$V_{DIS\_HYS}$	0.2	_	1.0	V	_
3.0.10	Input Current (Pull Up)	$I_{DIS}$	-200	-125	-50	μA	0 V < V <sub>DIS</sub> < 2.1 V
6.0.11		3.0	0	2	5	μΑ	V <sub>DIS</sub> > 3.0 V
5.0.12	Input Capacity <sup>1)</sup>	C <sub>DIS</sub>	_	_	20	pF	2)
3.0.13	Minimum Pulse Width <sup>1)</sup>	$t_{\sf DIS}$	0.4	0.8	1.5	μs	_
ABE		1				'	
6.0.14	Output low-level voltage	$V_{ABE\_OUTL}$	_	_	1.2	V	$V_{\rm DD\_THH} < V_{\rm DD} < 18~{\rm V}$ $I_{\rm ABE} < 5~{\rm mA}$
6.0.15			_	-	1.0	V	$ I_{\rm ABE} < 1~{\rm mA} $
5.0.16	Input threshold high	$V_{ABE\_INH}$	0.7*V <sub>DD</sub>	_	_	V	_
5.0.17	Input threshold low	$V_{ABE\_INL}$	_	_	0.3*V <sub>DD</sub>	V	_
3.0.18	Hysteresis	$V_{ABE\_INHY}$	0.2	_	1.0	V	_
5.0.19	Minimum pulse width <sup>1)</sup>	$t_{ABE}$	0.4	0.8	1.5	μs	_
6.0.20	ABE Input current (Pull	-I <sub>ABE_L</sub>	20	40	120	μΑ	1.5 V < V <sub>ABE</sub> < 18 V
6.0.21	Down)		0	_	60	μΑ	0 V < V <sub>ABE</sub> < 1.5 V
SI	I						· · · · · · · · · · · · · · · · · · ·
5.0.22	Low level	$V_{SI\_L}$	-0.3	_	1.0	V	_
5.0.23	High level	V <sub>SI_H</sub>	2.0	_	V <sub>DD</sub> +0.3	V	_
5.0.24	Hysteresis	$V_{SI\_HYS}$	0.2	_	1.0	V	_
5.0.25	Input Current (Pull Up)	$I_{SI}$	-30	-20	-10	μΑ	0 V < V <sub>SI</sub> < 2.1 V
3.0.26	Input Capacity <sup>1)</sup>	C <sub>SI</sub>	1		14	pF	2)



#### **Logic Inputs and Outputs**

#### **Electrical Characteristics: Control Inputs** (cont'd)

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V;  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	Test Conditions
			Min.	Тур.	Max.		
SCK							
6.0.27	Low level	$V_{SCK\_L}$	-0.3	_	1.0	V	_
6.0.28	High level	$V_{SCK\_H}$	2.0	_	V <sub>DD</sub> +0.3	V	_
6.0.29	Hysteresis	$V_{SCK\_HYS}$	0.2	_	1.0	V	_
6.0.30	Input Current (Pull Up)	$I_{SCK}$	-30	-20	-10	μA	$0 \text{ V} < V_{\text{SCK}} < 2.1 \text{ V}$
6.0.31	Input Capacity <sup>1)</sup>	C <sub>SCK</sub>	_	_	14	pF	2)
SS/SF							
6.0.32	Low level	$V_{\rm SS\_L}$	-0.3	_	1.0	V	_
6.0.33	High level	$V_{\rm SS\_H}$	2.0	_	V <sub>DD</sub> +0.3	V	_
6.0.34	Hysteresis	$V_{\rm SS\_HYS}$	0.2	-	1.0	V	_
6.0.35	Input Current in SPI	$I_{\rm SS}$	-30	-20	-10	μA	0 V < V <sub>SS</sub> < 2.1 V
6.0.36	mode (Pull Up)		-30	_	5	μA	2.1 V < V <sub>SS</sub> < 3.0 V
6.0.37			0	2	5	μA	V <sub>SS</sub> > 3.0 V
6.0.38	Input Current in SF	$I_{SF}$	0	2	5	μA	$V_{\rm SF}$ = 5.0 V, SF inactive
6.0.39	mode (Open Drain)		300	_	_	μA	$V_{\rm SF}$ = 1.0 V, SF active
6.0.40	Input Capacity <sup>1)</sup>	$C_{SS}$	_	_	15	pF	2)
so							
6.0.41	Low level	$V_{SO\_L}$	0.0	_	0.4	V	$I_{\rm SO}$ = 2 mA
6.0.42	High level	V <sub>SO_H</sub>	V <sub>DDIO</sub> -0.75	_	$V_{DDIO}$	V	$I_{\rm SO}$ = -2 mA 2.9 V < $V_{\rm DDIO}$ < 5.5 V
6.0.43	Output capacitance <sup>1)</sup>	$C_{SO}$	_	_	19	pF	In tristate <sup>2)</sup>
6.0.44	Leakage current	$I_{SO}$	-2	_	2	μА	In tristate $0 < V_{SO} < V_{DDIO}$

<sup>1)</sup> Not subject to production test; specified by design

<sup>2)</sup>  $V_{\text{bias}}$  = 2 V;  $V_{\text{test}}$  = 20 mVpp; f = 1 MHz



#### 7 Power Stages

The TLE8209-2SA contains four n-channel power-DMOS transistors that can be used in an H-bridge or in dual half bridge configuration.

Integrated circuits protect the outputs against overcurrent and over-temperature, in case of short-circuit to ground, to the supply voltage or across the load. Positive and negative voltage spikes, which occur when switching inductive loads, are limited by integrated freewheeling diodes (body diodes of power-DMOS).

#### 7.1 Parallel or SPI Control

By default the setting of the power switches is controlled by the Inputs IN1, IN2 (parallel control). The outputs OUT1 and OUT2 are set to High (high-side switch ON, low-side switch OFF) or Low (high-side switch OFF, low-side switch ON) by the parallel inputs IN1 and IN2, respectively. In SPI mode there is also the option to control the outputs via the SPI bits SIN1 and SIN2 of the SPI configuration register. To switch to SPI control the bit MUX has to be set to '0'.

In addition, the outputs can be disabled (set to tristate, high- and low-side switch OFF) by the disable input DIS and the bidirectional reset pin  $\overline{ABE}$ . Disabling sets the device to parallel control

**Table 1** shows the different options for the output control.

#### 7.2 H-Bridge or Single Switch Usage

The IC can be set to H-bridge mode or single-switch mode by SPI. This setting changes the behavior of the device in the following features:

- current limiting
- overcurrent shut-down
- · open load diagnosis

Table 1 Functional Truth Table

Pos.	DIS	ABE	IN1	IN2	SPI MUX	SPI SIN1	SPI SIN2	OUT1	OUT2
Forward, parallel ctrl.	L	Н	Н	L	1	X	X	Н	L
Reverse, parallel ctrl.	L	Н	L	Н	1	Х	Х	L	Н
Free-wheeling low, parallel ctrl.	L	Н	L	L	1	Х	Х	L	L
Free-wheeling high, parallel ctrl.	L	Н	Н	Н	1	Х	Х	Н	Н
Forward, SPI ctrl.	L	Н	Х	Х	0	1	0	Н	L
Reverse, SPI ctrl.	L	Н	Х	Х	0	0	1	L	Н
Free-wheeling low, SPI ctrl.	L	Н	Х	Х	0	0	0	L	L
Free-wheeling high, SPI ctrl.	L	Н	Х	Х	0	1	1	Н	Н
Disabled by DIS	Н	Х	Х	Х	Х	Х	Х	Z	Z
Disabled by ABE	Х	L	Х	Х	Х	Х	Х	Z	Z

Table 2 OUT States

OUT	High-Side DMOS	Low-Side DMOS	
Н	ON	OFF	
L	OFF	ON	
Z	OFF	OFF	



# 7.3 Electrical Characteristics Power Stages

#### **Electrical Characteristics: Power Stage**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	I	Limit Val	ues	Unit	<b>Test Conditions</b>	
			Min. Typ. Max		Max.			
Power (	Outputs OUT1, OUT2			•				
7.3.1	Switch on resistance low	$R_{OUT1L}$	_	125	_	$m\Omega$	$I_{\text{OUTx}} = 3 \text{ A}; T_{\text{j}} = 25^{\circ}\text{C}$	
	side	$R_{OUT2L}$	_	215	250		$I_{\text{OUTx}}$ = 3 A; $T_{\text{j}}$ = 150°C	
7.3.2	Switch on resistance high	$R_{OUT1H}$	_	115	_	mΩ	$I_{\text{OUTx}}$ = 3 A; $T_{\text{j}}$ = 25°C	
	side	$R_{OUT2H}$	_	200	240		$I_{\text{OUTx}}$ = 3 A; $T_{\text{j}}$ = 150°C	
7.3.3	Leakage current	$I_{ m OUT1(off)}$ $I_{ m OUT2(off)}$	-200	_	200	μΑ	Output stage switched off $V_S = 13 \text{ V}$	
7.3.4	Free-wheel diode forward voltage	$U_{D}$	_	0.9	1.1	V	I <sub>D</sub> = 3 A	
7.3.5	Free-wheel diode reverse recovery time <sup>1)</sup>	$t_{rr}$	_	_	100	ns	_	
Output	Switching Times - Fast Sle	w Rate						
7.3.6	Rise time HS	t <sub>r (HS)</sub>	3.5	6.0	10	μS	SPI bit SL='0'	
7.3.7	Fall time HS	t <sub>f (HS)</sub>	3.5	6.0	10		$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.8	Rise time LS	t <sub>r (LS)</sub>	3.5	6.0	8.5			
7.3.9	Fall time LS	$t_{f(LS)}$	3.5	6.0	8.5			
Output	Switching Times - Slow Sle	w Rate						
7.3.10	Rise time HS	$t_{r  (HS)}$	15	30	48	μS	SPI bit SL='1'	
7.3.11	Fall time HS	$t_{f(HS)}$	15	30	48		$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.12	Rise time LS	$t_{r (LS)}$	18	30	48			
7.3.13	Fall time LS	$t_{f(LS)}$	18	30	48			
Output	Delay - Parallel Control, Fa	st Slew Rat	:e					
7.3.14	Output on-delay	$t_{\sf don}$	_	_	12	μS	$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.15	Output off-delay	$t_{doff}$	_	_	7	μS		
Output	Delay - SPI Control, Fast S	lew Rate						
7.3.16	Output on-delay	$t_{\sf don}$	_	_	13	μS	$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.17	Output off-delay	$t_{doff}$	_	_	12			
Output	Delay - Parallel Control, Slo	ow Slew Ra	te					
7.3.18	Output on-delay	$t_{\sf don}$	_		41	μS	$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.19	Output off-delay	$t_{doff}$	_	_	25			
Output	Delay - SPI Control, Slow S	Slew Rate						
7.3.20	Output on-delay	$t_{\sf don}$	_	_	42	μS	$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.21	Output off-delay	$t_{doff}$	_	_	26			



#### **Electrical Characteristics: Power Stage**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	<b>Test Conditions</b>	
			Min.	Тур.	Max.			
Enable	and Disable Delay Times			"				
7.3.22	Disable delay time, fast slew rate	$t_{\sf ddis}$	_	8	20	μS	$V_{\rm S}$ = 818 V; $I_{\rm OUT}$ = 3 A	
7.3.23	Disable delay time, slow slew rate	$t_{ m ddis}$	_	38	75			
7.3.24	Enable delay time, fast slew rate	$t_{del}$	_	8	20			
7.3.25	Enable delay time, slow slew rate	$t_{del}$	_	38	75			
7.3.26	Power on delay time	$t_{ m del}$	_	0.1	0.4	ms	$V_{\rm S}$ = on> output stage active, no load	

<sup>1)</sup> Not subject to production test - specified by design




Figure 5 Output Switching Time




Figure 6 Output Delay Time - Low-Side FETs






Figure 7 /ABE pin - Enable and Disable Delay Time




Figure 8 DIS pin - Enable and Disable Delay Time



# 8 Protection and Monitoring

Both output stages of the TLE8209-2SA are equipped with fault diagnostic functions:

- Short to battery voltage (SCB). Can be detected when low side-switches are turned on
- Short to ground (SCG). Can be detected when high side-switches are turned on
- · Open load (OL). Can be detected in inactive mode
- Over-temperature (OT). Can be detected in active and inactive mode
- VDD over- and under voltage (Chapter 5.2)
- · Battery under voltage detection. Can be detected in active and inactive mode

Individual detection for each output in single switch operation mode (SCB, SCG, OL) is possible. The corresponding diagnostics bits for each failure will be set in the SPI according to **Table 8 "Failure Encoding" on Page 29**.

#### 8.1 Diagnosis in Status Flag Mode

Instead of using the SPI interface for control and diagnosis of the TLE8209-2SA, the device can also be set into status flag mode by connecting pin VDDIO to GND as described in **Chapter 5.3**.

In status flag mode the pin SF will be pulled low in the following cases:

- undervoltage at VS
- bridge disabled by ABE or DIS
- bridge disabled by VDD monitoring
- bridge disabled by short circuit detection
- overtemperature shut down

SF will not be pulled low if  $V_{DD}$  is below the power on reset threshold (VDD\_POR).

#### 8.2 Current Limitation

To limit the output current at low power loss, a chopper current limitation is integrated. Current measurement for current limitation is done in the high side path. This requires high side freewheeling in case of active current limitation.




Figure 9 Chopper Current Limitation

**Figure 9** shows the behavior of the current limitation for over current detection in HS1. It applies accordingly also for HS2:

When the current in high-side switch of OUT1 (HS1) exceeds the limit  $I_L$  longer than the blanking time  $t_b$ , OUT2 is switched to high (e.g. LS2->OFF, HS2->ON), independent of the input signal at IN2. This leads to a slow-decay current decrease in the load and in HS1. As soon as the current falls below  $I_L$ - $I_{hvs}$ , OUT2 is switched back to normal



operation, i.e. the outputs follow the inputs according to the truth table. The current limit  $I_L$  can be programmed to four different values by setting the SPI bits CL1 and CL2 in the SPI configuration register. To avoid high chopper frequencies the time between two transients  $t_{trans}$  is limited.

Current limitation is available in H-bridge operation mode, not in single switch operation mode. This means, that the current limit, current limit hysteresis and blanking time has no effect in single switch operation mode.

#### 8.3 Temperature Dependent Current Reduction

For  $T_{\rm ILR} < T_{\rm j} < T_{\rm SD}$  the current limit decreases from  $I_{\rm L}$  as set by the SPI to  $I_{\rm L\_TSD}$  = 2.5 A typ. as shown in Figure 10.




Figure 10 Temperature Dependent Current Reduction

#### 8.4 Short Circuit to Ground




Figure 11 Short to Ground Detection



The short circuit to ground detection is activated when the current through one of the high side switches rises over the threshold  $I_{OUK}$  and remains higher than  $I_{OUK}$  for at least the filter time  $t_{DF}$  H within the blanking time  $t_b$ .

The output stage in which the short circuit was detected will be switched off within t<sub>DF OFF</sub>.

In H-bridge mode also the other output will be switched off after a short delay of  $t_{\text{DF del}}$  .

In single switch mode only the affected output will be switched off.

#### 8.5 Short Circuit to Battery

A short circuit to battery is detected in the same way as a short circuit to ground, only in the low side switch instead of the high side switch.

#### 8.6 Short Circuit across the Load

Short circuit over load is indicated by two failures - short circuit to ground on one output and short circuit to battery on the other output. Both failure bits will be set in the SPI diagnostics register. Both output stages will be turned off.

#### 8.7 Overtemperature

In case of high DC-currents, insufficient cooling or high ambient temperature, the chip temperature may rise above the thermal shut-down temperature  $T_{\rm SD}$  (see **Figure 10**). In that case, all output transistors are turned off.

#### 8.8 Undervoltage Shut-Down

If the supply voltage at the VS pins falls below the undervoltage detection threshold  $V_{UV\_OFF}$ , the outputs switches are turned off. As soon as  $V_S$  rises above  $V_{UV\_ON}$  again, the device is returning to normal operation.

#### 8.9 Open Load Diagnosis

Open load diagnosis is only possible if outputs are switched off by DIS or  $\overline{ABE}$ . The diagnostic current sources are deactivated in status flag mode. Diagnostic current sources are disconnected if outputs are active. That means that the diagnostic current sources are also disconnected if the outputs are deactivated due to short circuit. The open load detection in H-bridge mode is different from the open load detection in single switch mode.

#### Open Load Detection in H-Bridge mode




Figure 12 Open Load Detection in H-Bridge Mode



Table 3 Open Load Detection in H-Bridge Mode

VOUT1	OUT1_L	VOUT2	OUT2_L	Diagnostic	Comment
< V <sub>ref_L</sub>	Н	< V <sub>ref_L</sub>	Н	Load o.k.	pull down current is stronger
< V <sub>ref_L</sub>	Н	> V <sub>ref_L</sub>	L	Load o.k.	transient area
> V <sub>ref_L</sub>	L	< V <sub>ref_L</sub>	Н	Open Load	
> V <sub>ref_L</sub>	L	> V <sub>ref_L</sub>	L	Load o.k.	transient area

#### **Open Load Detection in Single Switch Mode**




Figure 13 Open Load Detection in Single Switch Mode

Table 4 Open Load Detection in Single Switch Mode

VOUTx (OFF State)	OUTx_H	OUTx_L	Diagnostic	Comment
$\overline{V_{\rm OUTx}} < V_{\rm ref\_L}$	L	Н	o.k.	Load to ground
$\overline{V_{\text{ref\_L}} < V_{\text{OUTx}} < V_{\text{ref\_H}}}$	L	L	Open Load	Output open
$V_{\text{OUTx}} > V_{\text{ref\_H}}$	Н	L	o.k.	Load to V <sub>S</sub>



#### 8.10 Electrical Characteristics

#### **Electrical Characteristics: Protection and Monitoring**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol		Limit Va	alues	Unit	Test Conditions	
			Min.	Тур.	Max.			
Choppe	r Current Limitation							
8.10.1	Current Limit	$ I_{L1} $	1.0	1.5	2.0	Α	$-40  ^{\circ}\text{C} < T_{\text{j}} < T_{\text{ILR}}$	
8.10.2		$ I_{L2} $	3.3	4.0	4.7		Dependent on SPI	
8.10.3		$ I_{L3} $	5.5	6.6	7.7		setting; Default = I <sub>L3</sub>	
8.10.4		$ I_{L4} $	7.7	8.6	10.0			
8.10.5	Current Limit Hysteresis	$I_{hys}$	0	0.25	0.40	Α	$-40  ^{\circ}\text{C} < T_{\text{j}} < T_{\text{ILR}}$	
8.10.6	Blanking time	$t_{b}$	8	11	15	μS	_	
8.10.7	Time between transients	$t_{trans}$	90	_	130	μS	_	
	ature Dependent Current L							
8.10.8	Current Limit at T <sub>SD</sub>	$I_{L\_TSD}$	1.4	2.5	3.6	Α	_	
8.10.9	Start of current limit reduction	$T_{ILR}$	150	165	_	°C	_	
8.10.10	Thermal shut-down	$T_{SD}$	175	_	_	°C	_	
8.10.11	Range of temperature dependent current reduction	T <sub>SD</sub> - T <sub>ILR</sub>	20	25	30	°C	_	
Short C	ircuit Detection to GND							
8.10.12	Short circuit detection	$ I_{OUKH1} $	2.5	5.0	6.5	Α	-40 °C < T <sub>i</sub> < T <sub>ILR</sub>	
8.10.13	current (HS)	$ I_{OUKH2} $	5.0	7.3	10		Dependent on SPI-	
8.10.14	_	$ I_{\text{OUKH3}} $	7.5	9.5	11.5		setting for $ I_L $ ; Default =	
8.10.15		$ I_{\text{OUKH4}} $	9.5	11.8	17.4		$I_{OUKH3}$	
8.10.16	Current tracking	I <sub>OUKH1</sub>   -  I <sub>L1</sub>	2.0	3.5	5.0	Α		
8.10.17		$ I_{\text{OUKH2}}  -  I_{\text{L2}} $	2.0	3.3	5.0			
8.10.18		$ I_{\text{OUKH3}}  -  I_{\text{L3}} $		3.2	5.0			
8.10.19		$ I_{\text{OUKH4}}  -  I_{\text{L4}} $	1.8	3.0	5.0			
Short C	ircuit Detection to VS							
8.10.20	Short circuit detection	$ I_{OUKL1} $	2.5	4.6	6.5	Α	$-40  ^{\circ}\text{C} < T_{\text{j}} < T_{\text{ILR}}$	
8.10.21	current (LS)	$ I_{\text{OUKL2}} $	5.0	7.9	10		Dependent on SPI-	
8.10.22		$ I_{\text{OUKL3}} $	7.5	9.8	11.5		setting for $ I_L $ ; Default =	
8.10.23		$ I_{OUKL4} $	9.5	14	17.4		$I_{OUKL3}$	
8.10.24	Current tracking	$ I_{\text{OUKL1}}  -  I_{\text{L1}} $	1.5	3.0	5.0	Α		
8.10.25		$ I_{\text{OUKL2}} $ - $ I_{\text{L2}} $	2.0	4.0	5.5			
8.10.26		$ I_{\text{OUKL3}} $ - $ I_{\text{L3}} $	1.8	3.5	5.5			
8.10.27		$ I_{\text{OUKL4}}  -  I_{\text{L4}} $	2.0	5.1	8.0			



#### **Electrical Characteristics: Protection and Monitoring**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	t Test Conditions	
			Min.	Тур.	Max.			
Short Ci	rcuit Detection Timing							
8.10.28	Delay time for fault detection	$t_{DF\_H}, t_{DF\_L}$	1	2	5	μs	_	
8.10.29	Time from detected fault to high impedance of output <sup>1)</sup>	$t_{DF\_OFF}$	_	_	4	μs	-	
8.10.30	Delay time between switching off of the output stages in short circuit	t <sub>DF_del</sub>	5	17	40	μs	_	
Open Lo	oad	1				•		
8.10.31	Open Load Diagnostic Filter Time <sup>1)</sup>	$t_{OL\_DIAG}$	60	-	135	μs	_	
8.10.32	Low Diagnosis Threshold	V <sub>ref_L</sub>	0.4 * V <sub>DD</sub> - 0.2	0.4 * V <sub>DD</sub>	0.4 * V <sub>DD</sub> + 0.2	V	-	
8.10.33	High Diagnosis Threshold	V <sub>ref_H</sub>	0.8 * V <sub>DD</sub> - 0.2	0.8 * V <sub>DD</sub>	0.8 * V <sub>DD</sub> + 0.2	V	_	
8.10.34	Diagnosis Bias Voltage	V <sub>ref_M</sub>	0.6 * V <sub>DD</sub> - 0.2	0.6 * V <sub>DD</sub>	0.6 * V <sub>DD</sub> + 0.2	V	_	
8.10.35	Positive Diagnostic Current	I <sub>DIA_P</sub>	300	620	980	μΑ	V <sub>OUTx</sub> = 14 V	
8.10.36	(pull down current source)	_	270	610	980	μΑ	$V_{\text{OUTx}} = V_{\text{ref\_H}}$	
8.10.37	Negative Diagnostic	I <sub>DIA_N</sub>	-350	-240	-100	μΑ	V <sub>OUTx</sub> = 0 V	
8.10.38	Current		-350	-210	-80	μΑ	$V_{\text{OUTx}} = V_{\text{ref\_L}}$	
8.10.39	Ratio of current sources (Pos/Neg)	Ratio <sub>I_DIA</sub>	2	2.9	4	-	-	
Undervo	oltage			·				
8.10.40	Undervoltage at $V_{\rm S}$	$V_{UVOFF}$	3.1	3.7	4.4	V	Switch off threshold	
		$V_{UVON}$	3.3	3.9	4.6	V	Switch on threshold	
		$V_{UVHY}$	100	200	400	mV	Hysteresis	
8.10.41	VS Undervoltage Detection Filter Time <sup>1)</sup>	$t_{\sf UV}$	_	-	1.5	μs		

<sup>1)</sup> Not subject to production test; specified by design.



#### 9 SPI Interface

The serial SPI interface establishes a communication link between TLE8209-2SA and the systems microcontroller. The TLE8209-2SA always operates in slave mode whereas the controller provides the master function. The maximum baud rate is 2 MBaud.

By applying an active slave select signal at  $\overline{SS}$  the TLE8209-2SA is selected by the SPI-master. SI is the data input (Slave In), SO the data output (Slave Out). Via SCK (Serial Clock Input) the SPI-clock is provided by the master. In case of inactive slave select signal (High) the data output SO goes into tristate.

The first two bits of an instruction may be used to establish an extended device-addressing. This gives the opportunity to operate up to 4 Slave-devices sharing one common SS signal from the Master-Unit (see Figure 16).




Figure 14 SPI Block Diagram

#### 9.1 General SPI Characteristics

- 1. During active reset conditions the SPI is driven into its default state. The output SO is set to high impedance (tristate). When reset becomes inactive, the state machine enters into a wait state for the next instruction.
- 2. If the slave select signal at SS is inactive (high), the state machine is forced to wait for the following instruction.
- 3. During active (low) state of the select signal SS the falling edge of the serial clock signal SCK will be used to latch the input data at SI. Output data at SO are driven with the rising edge of SCK. Further processing of the data according to the instruction (i.e. modification of internal registers) will be triggered by the rising edge of the SS signal.
- 4. In order to establish the option of extended addressing the upper two bits of the instruction byte (i.e. the first two SI bits of a frame) are reserved to send a chip address. To avoid a bus conflict the output SO will remain tristate during the addressing phase of a frame (i.e. until the address bits are recognized as a valid chip



address). If the chip address does not match, the according frame will be ignored and SO remains tristate for the complete frame.

- 5. Verification byte: Simultaneously to the receipt of an SPI instruction the TLE8209-2SA transmits a verification byte via the output SO to the controller. This byte indicates regular or irregular operation of the SPI. It contains an initial bit pattern and a flag indicating an invalid instruction of the previous access.
- 6. On a read access the data bits at the SPI input SI are rejected. During a valid write access the SPI will transmit the data byte "00hex" at the output SO after having sent the verification byte.
- 7. An instruction is invalid if one of the following conditions is fulfilled:
  - an unused instruction code is detected (see tables with SPI instructions).
  - the previous transmission is not completed in terms of internal data processing.
  - the number of SPI clock pulses (falling edge) counted during active SS differs from exactly 16 clock pulses. If an unused instruction code occurres, the data byte "FF<sub>hex</sub>" (no error) will be transmitted after having sent the verification byte. This transmission takes place within the same SPI-frame that contained the unused instruction byte.

If an invalid instruction is detected, bit TRANS\_F in the following verification byte (next SPI-transmission) is set to HIGH. The TRANS\_F bit must not be cleared before it has been sent to the microcontroller.

#### 9.2 SPI Communication

The 16 input bits consist of the SPI instruction byte and an input data byte. The 16 output bits consist of the verification byte and the output data byte (see also **Figure 15**). The definition of these bytes is given in the subsequent sections. The access mode of the registers is described in the column "Type" (r = read, w = write).




Figure 15 SPI Communication

#### 9.2.1 Instruction Byte

The upper 2 bit of the instruction byte contain the chip address. The chip address of the TLE8209-2SA is '00'. During read access, the output data according to the register requested in the instruction byte are applied to SO within the same SPI frame. That means, the output data corresponding to an instruction byte sent during one SPI frame are transmitted to SO during the same SPI-frame



Table 5 SPI Instruction Format

7	6	5	4	3	2	1	0
CPAD1	CPAD0	INSTR5	INSTR4	INSTR3	INSTR2	INSTR1	INSTR0

Field	Bits	Туре	Description
CPAD1:0	7:6	w	Chip Address (00 <sub>B</sub> )
INSTR5:0	5:0	w	SPI Instruction (encoding)




Figure 16 Bus Arbitration by Chip Address



Table 6 SPI Instruction Set

Command	SPI Instruction Byte	Description
RD_ID	0000 0000	Read identifier
RD_REV	0000 0011	Read version
RD_DIA	0000 1001	Read diagnostics register
RD_CONFIG	0011 0000	Read power stage configuration
RD_STATCON	0011 1100	Read VDD monitoring status
WR_CONFIG	0010 1000	Write power stage configuration
WR_STATCON	0001 1000	Write VDD monitoring status
all other instructions	00xx xxxx	Unused - TRANS_F is set to high, ff_hex is sent as data bit.
all other chip addr.	XXXX XXXX	Invalid address - SO remains tristate during entire SPI-frame.

#### 9.2.2 Verification Byte

Table 7 Verification Byte Format

7	6	5	4	3	2	1	0	
VER6	VER5	VER4	VER3	VER2	VER1	VER0	TRANS_F	

Field	Bits	Type	Description
VER6	7	r	Fixed to tristate (Z)
VER5	6	r	Fixed to tristate (Z)
VER4	5	r	Fixed to high (1)
VER3	4	r	Fixed to low (0)
VER2	3	r	Fixed to high (1)
VER1	2	r	Fixed to low (0)
VER0	1	r	Fixed to high (1)
TRANS_F 0 r			Transfer failure:
			1 <sub>B</sub> Error detected during previous transfer
			0 <sub>B</sub> Previous transfer was recognized as valid

#### 9.2.3 Device Identifier and Revision

The IC's identifier (device ID) and revision number are used for production test purposes and features plug & play functionality depending on the systems software release. The two numbers are read-only accessible via the SPI-instructions RD\_ID and RD\_REV as described in **Section 9.2.1**. The device ID is defined to allow identification of different IC-types by software and is fixed for the TLE8209-2SA.

The revision number may be utilized to distinguish different states of hardware and is updated with each redesign of the TLE8209-2SA. It is divided into an upper 4 bit field reserved to define revisions (SWR) corresponding to specific software releases and a lower 4 bit field utilized to identify the actual mask set revision (MSR).



#### ID\_REG

#### **Device Identifier**

7	6	5	4	3	2	1	0
ID7	ID6	ID5	ID4	ID3	ID2	ID1	ID0

Field	Bits	Туре	Description
ID7:0	7:0	r	Device-ID
			TLE8209-2SA: DE hex

# REV\_REG Device Revision

7	6	5	4	3	2	1	0	
SWR3	SWR2	SWR1	SWR0	MSR3	MSR2	MSR1	MSR0	

Field	Bits	Туре	Description
SWR3:0	7:4	r	Revision corresponding to software release
MSR3:0	3:0	r	Revision corresponding to mask set

# 9.2.4 Diagnostics Register

#### DIA\_REG

Diagnostics Register Reset Value: x111 1111<sub>B</sub>

7	6	5	4	3	2	1	0	
ABE/DIS	ОТ	CurrRed	CurrLim	DIA21	DIA20	DIA11	DIA10	

Field	Bits	Type	Description
ABE/DIS	7	r	Is set to "0" in case of ABE = L or DIS = H
OT	6	r	Is set to "0" in case of over temperature
CurrRed	5	r	Is set to "0" in case of temperature dependent current limitation
CurrLim	4	r	Is set to "0" in case of current limitation
DIA21	3	r	Diagnosis-Bit2 of OUT2
DIA20	2	r	Diagnosis-Bit1 of OUT2
DIA11	1	r	Diagnosis-Bit2 of OUT1
DIA10	0	r	Diagnosis-Bit1 of OUT1



Table 8 Failure Encoding

ABE/DIS	DIA21	DIA20	DIA11	DIA10	Description	Comment
Х	1	1	1	1	no failure	
1	Х	Х	0	1	short circuit to battery at OUT1 (SCB1)	latched
1	Х	Х	1	0	short circuit to ground at OUT1 (SCG1)	latched
1	Х	Х	1	1	no error detected at OUT1	
1	0	1	Х	Х	short circuit to battery at OUT2 (SCB2)	latched
1	1	0	Х	Х	short circuit to ground at OUT2 (SCG2)	latched
1	1	1	Х	Х	no error detected at OUT2	
1	0	1	1	0	short circuit accross load (HS1+LS2 active)	latched
1	1	0	0	1	short circuit accross load (HS2+LS1 active)	latched
X	0	0	0	0	Undervoltage at pin VS	not latched
0	1	1	0	0	open load (H-Bridge)	latched
0	1	1	Х	0	open load at OUT1 (single switch operation)	latched
0	1	1	0	Х	open load at OUT2 (single switch operation)	latched

#### Note:

The bit ABE/DIS shows directly the status of inputs ABE and DIS. It is set to '0' if the power stages are disabled by ABE or DIS.

The bits OT, CurrRed and CurrLim are latched. They will be reset with each read access. If the failure condition is still present the according bits are set again.

Undervoltage at VS is reported and the outputs are switched off as long as the undervoltage condition is present. The previous setting of the DIAx bits is masked but not reset. Once the supply voltage is back in the operating range the diagnostic bits DIAxx will return to their setting before VS undervoltage. The outputs will return to normal operation.

Detection of short circuit will switch of the output stages. In single half bridge operation only the affected output is switched off. In H-Bridge mode both outputs are shut down. The outputs remain off until the failure condition is removed and the diagnosis register is reset.

A short across the load may also be reported as SCG at one output and SCB at the other.

The diagnostic information DIAxx in the SPI interface is reset in the following cases:

- Read out of DIA\_REG: only bit 4, 5 and 6 will be reset
- Enabling or disabling of the bridge via ABE or DIS
- Undervoltage at VDD
- Reset command via SPI



# 9.2.5 Configuration Register

#### CONFIG\_REG

Configuration Register Reset Value: 1111 1010<sub>B</sub>

7	6	5	4	3	2	1	0	
MODE	MUX	SIN1	SIN2	CL1	CL2	RESET	SL	

Field	Bits	Туре	Description
MODE	7	wr	'1': H-bridge mode
			'0': single output stages (for current levels 1 to 3 only)
MUX	6	wr	'1': control by parallel inputs IN1 and IN2
			'0': control by SPI bits SIN1 and SIN2
SIN1	5	wr	control of OUT1 if MUX='0'
SIN2	4	wr	control of OUT2 if MUX='0'
CL1	3	wr	current limitation level (see table below)
CL2	2	wr	current limitation level (see table below)
RESET	1	wr	'0': reset of digital logic
SL	0	wr	slew rate setting
			'1': slow
			'0': fast

#### **Table 9** Current Limitation Levels

CL1	CL2	Current Level	Typical Current
0	0	1	1.5A
0	1	2	4.0A
1	0	3 (default)	6.6A
1	1	4	8.6A

# 9.2.6 STATCON Register

# STATCON\_REG

STATCON Register Reset Value: 1101 1xxx<sub>B</sub>

7	6	5	4	3	2	1	0
CONFIG2	CONFIG1	CONFIG0	DIACLR2	DIACLR1	STATUS2	STATUS1	STATUS0

Field	Bits	Type	Description
CONFIG2	7	wr	VDD threshold test mode
			'1': VDD monitoring in normal operation
			'0': VDD thresholds are changed according to CONFIG1



Field	Bits	Type	Description
CONFIG1	6	wr	changes thresholds in VDD threshold test mode (CONFIG2='0') '1': increase lower threshold of VDD monitoring to test switch off path '0': decrease upper threshold of VDD monitoring to test switch off path
CONFIG0	5	wr	latch function for overvoltage at VDD '1': overvoltage at VDD latched '0': overvoltage at VDD not latched
DIACLR2	4	wr	'0': clears diagnosis of OUT2 always returns '1' at read access
DIACLR1	3	wr	'0': clears diagnosis of OUT1 always returns '1' at read access
STATUS2	2	r	returns level at ABE
STATUS1	1	r	'0': under voltage at VDD '1': VDD voltage above lower limit
STATUS0	0	r	0': over voltage at VDD '1': VDD voltage below upper limit



#### 9.2.7 Contents of the SPI registers after a reset condition

Note: The registers for device identifier and revision (ID\_REG and REV\_REG) are not affected by reset.

#### DIA\_REG

	7	6	5	4	3	2	1	0
	ABE/DIS	ОТ	CurrRed	CurLim	DIA21	DIA20	DIA11	DIA10
POR	Х	1	1	1	1	1	1	1
SPIR	х	1	1	1	1	1	1	1
ABE/DISR	Х	1	1	1	1	1	1	1
RDR	х	1	1	1	Х	Х	Х	Х
DIACLR1	Х	Х	х	Х	Х	Х	1	1
DIACLR2	х	Х	х	х	1	1	х	Х

#### CONFIG\_REG

	7	6	5	4	3	2	1	0
	MODE	MUX	SIN1	SIN2	CL1	CL2	RESET	SL
POR	1	1	1	1	1	0	1	0
SPIR	1	1	1	1	1	0	1	0
DISR	Х	1	1	1	Х	Х	1	Х
SFMODE	1	1	1	1	1	0	1	0

#### STATCON\_REG

	7	6	5	4	3	2	1	0
	CONFIG2	CONFIG1	CONFIG0	DIACLR2	DIACLR1	STATUS2	STATUS1	STATUS0
POR	1	1	0	1	1	Х	х	Х
SPIR	1	1	0	1	1	Х	Х	Х
SFMODE	1	1	0	1	1	х	х	Х

POR: Reset due to VDD power up

SPIR: Reset via SPI by writing 0 into the RESET of CONFIG\_REG

ABE/DISR: Reset due to enabling or disabling the power stages via DIS or ABE (edge triggered)

DISR: Reset due to a disabled power stage by DIS or ABE (level triggered)

RDR: Reset due to a read access to DIA\_REG

DIACLR1: Reset via SPI by writing 0 into the DIACLR1 of STATCON\_REG DIACLR2: Reset via SPI by writing 0 into the DIACLR2 of STATCON\_REG

SFMODE: Reset by setting the TLE8209-2SA into the Status Flag Mode (VDDIO = 0V)

x: No change

Note: If a reset condition is not listed for a particular register it has no effect on the contents of this register.



#### 9.3 Electrical Characteristics SPI

#### **Electrical Characteristics: SPI Interface**

 $V_{\rm S}$  = 5 V to 28 V;  $V_{\rm DD}$  = 5.0 V;  $V_{\rm DDIO}$  = 2.9 V to 5.5 V,  $T_{\rm j}$  = -40 ·C to 150 ·C, all voltages with respect to ground, positive current flowing into pin (unless otherwise specified)

Pos.	Parameter	Symbol	Limit Values			Unit	<b>Test Conditions</b>	
			Min.	Тур.	Тур. Мах.			
SPI-Tim	ning (see Figure 17) <sup>1)</sup>	l l						
9.3.1	Cycle-time (1)	$t_{ m cyc}$	490	_	_	ns	referred to master	
9.3.2	Enable Lead Time (2)	$t_{lead}$	50	_	_	ns	referred to master	
9.3.3	Enable Lag Time (3)	$t_{\text{lag}}$	150	_	_	ns	referred to master	
9.3.4	Data Valid (4) H->L: $V_{SCK}$ =2V -> $V_{SO}$ =0.2 $V_{DDIO}$ L->H: $V_{SCK}$ =2V -> $V_{SO}$ =0.8 $V_{DDIO}$ if $V_{DDIO}$ < 4.5V: L->H: $V_{SCK}$ =2V -> $V_{SO}$ =0.7 $V_{DDIO}$	$t_{ m v}$	_	_	150 230	ns	$C_{\rm L}$ = 200 pF $C_{\rm L}$ = 350 pF referred to TLE8209-2	
9.3.5	Data Setup Time (5)	$t_{su}$	40	_	_	ns	referred to master	
9.3.6	Data Hold Time (6)	$t_{h}$	40	_	_	ns	referred to master	
9.3.7	Disable Time (7)	$t_{\sf dis}$	_	_	100	ns	referred to TLE8209-2	
9.3.8	Transfer Delay (8)	$t_{dt}$	250	_	_	ns	referred to master	
9.3.9	Disable Lead Time (9)	$t_{\sf dld}$	250	_	_	ns	referred to master	
9.3.10	Disable Lag Time (10)	$t_{ m dlg}$	250	_	_	ns	referred to master	
9.3.11	Access time (11)	$t_{\rm acc}$	8.35	_	_	μS	referred to master	

<sup>1)</sup> All timing parameters specified by design - not subject to production test




Figure 17 SPI Timing



**Application Information** 

# 10 Application Information

Note: The following simplified application examples are given as a hint for the implementation of the device only and shall not be regarded as a description or warranty of a certain functionality, condition or quality of the device. The function of the described circuits must be verified in the real application




Figure 18 Application Example H-Bridge with SPI-Interface



#### **Application Information**




Figure 19 Application Example with Status Flag




Figure 20 Application Examples for Overvoltage and Reverse-Voltage Protection

Package Outlines TLE8209-2SA

# 11 Package Outlines TLE8209-2SA




Figure 21 PG-DSO-20-65 (Plastic Dual Small Outline Package)

#### **Green Product (RoHS compliant)**

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pb-free finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).

You can find all of our packages, sorts of packing and others in our Infineon Internet Page: http://www.infineon.com/packages

Dimensions in mm



**Revision History** 

# 12 Revision History

Revision	Date	Comments / Changes Initial Product Proposal					
0.1	2008-08-21						
0.2	2008-12-05	- General: Package PG-DSO-20-37 (TLE8209-2SA) added					
		- Page 13, Chapter 6: Description of digital inputs modified					
		- Page 14, Pos. 6.0.36 & 6.0.37: typ. values removed					
		- Page 16: Switching times adjusted to TLE8209-1 values					
		- Page 36ff: Application diagrams updated (Figures 19 & 20)					
		- Page 38: Package drawing added					
		- Page 39: Package drawing updated					
0.3	2009-07-31	Target Data Sheet					
		- General: Package names changed					
		- Page 24, Pos. 8.10.5, current limit hysteresis min. changed					
0.4	2009-12-11	Preliminary Data Sheet					
		- Limits revised throughout the whole document					
		- Cover: Subtitle changed to "SPI Programmable H-Bridge"					
		- Page 3: Feature List and Functional Description revised					
		- Page 17ff: Rearranged figures 6 to 9					
		- Page 20: Figures 11 & 12 revised					
		- Page 21: Short circuit description revised					
		- Page 36: Application Diagram with Status Flag (Figure 20) updated					
		- Page 38: Package Drawing updated					
1.0	2010-02-16	Data Sheet					
		- General: Single package version: PG-DSO-20-65 (PowerSO20) only.					
		- Page 3, Overview: added "low standby current" in feature list					
		- Page 11, Pos. 5.4.1: Parameter name changed to "Supply Current";					
		- Page 11, Pos. 5.4.1: added limits for I <sub>VS</sub> at V <sub>DD</sub> = 0V.					
		- Page 19, Figure 11 updated.					
1.2	2012-12-20	- Page3: Feature list revised					
		- Page 22, Pos. 8.10.4:  I <sub>1.4</sub>   max. changed from 10.5A to 10.0A					
		- Page 27, Chapter 9.2.3: Description of device identifier and revision modified					

Edition 2012-12-20

Published by Infineon Technologies AG 81726 Munich, Germany © 2012 Infineon Technologies AG All Rights Reserved.

#### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

#### Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

#### Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.