

PSOC™ 4000T MCU registers

Reference manual

About this document

Scope and purpose

The document discusses the PSOC™ 4000T registers lists all the registers in mapping tables, in address order. For architecture details, see [PSOC™ 4000T MCU architecture reference manual](#).

Intended audience

This document is intended for the system designers, programmers, and so on, who are designing, or programming using PSOC™ 4000T registers.

Table of contents

Table of contents

About this document	1
Scope and purpose	1
Intended audience	1
Table of contents	2
Register mapping	3
Register general conventions	3
Acronyms	3
1 Supervisory Flash registers	7
1.1 Register details	7
2 Peripheral registers	29
2.1 Register details	29
3 High Speed IO Matrix (HSIOM) registers	39
3.1 Register details	39
4 System Resources Subsystem (SRSS) registers	47
4.1 Register details	47
5 General Purpose IO (GPIO) registers	76
5.1 Register details	76
6 CPU Sub System (CPUSS) registers	115
6.1 Register details	115
7 SPC Interface (SPCIF) registers	126
7.1 Register details	126
8 Timer, Counter, PWM (TCPWM) registers	133
8.1 Register details	133
9 Serial Communication Block (SCB) registers	158
9.1 Register details	158
10 CAPSENSE™ registers	256
11 Cortex M0+ (CM0P) registers	257
11.1 Register details	257
12 ROM Table registers	320
12.1 Register details	320
Revision history	335

Register mapping

Register mapping

The PSOC™ 4 device requires peripheral register accesses to match the hardware register size.

Otherwise, the peripheral might ignore the transfer and hard fault exception will be generated. It is recommended to use the APIs provided by the [core library](#) or accessing the registers.

Register general conventions

The register conventions specific to this section and the Register Reference chapter are listed in this table.

Convention	Description	Explanation
'x' in a register name	ACBxxCR1	multiple instances/address ranges of the same register
R	R: 00	read register or bit(s)
W	W: 00	write register or bit(s)
WOC	WOC:0	write one to clear
WZC	WZC:0	write zero to clear
RC	RC:0	read to clear
WC	WC:0	write to clear
NA	NA:000	reserved
U	R:U	undefined
Retention	Retention: Retained	These registers will hold their values even in deepsleep while the others won't.

Acronyms

This table lists the acronyms used in this document.

Table 1 Acronyms

Symbol	Unit of measure
ABUS	analog output bus
AC	alternating current
ADC	analog-to-digital converter
AHB	AMBA (advanced microcontroller bus architecture) high-performance bus, an Arm® data transfer bus
API	application programming interface
APOR	analog power-on reset
BC	broadcast clock
BOM	bill of materials
BR	bit rate
BRA	bus request acknowledge
BRQ	bus request
CAN	controller area network
CI	carry in

Acronyms

Table 1 **Acronyms** (continued)

Symbol	Unit of measure
CMP	compare
CO	carry out
CPU	Central Processing Unit
CRC	cyclic redundancy check
CSD	CAPSENSE™ sigma delta
CT	continuous time
CTBm	continuous time block-mini
DAC	digital-to-analog converter
DC	direct current
DI	digital or data input
DMA	direct memory access
DNL	differential nonlinearity
DO	digital or data output
DSI	digital signal interface
DSM	Deep Sleep mode
ECO	External Crystal Oscillator
EEPROM	electrically erasable programmable read only memory
EMIF	external memory interface
FB	feedback
FIFO	first-in first-out
FSR	full scale range
GPIO	general purpose I/O
HCI	Host-Controller Interface
HFCLK	high-frequency clock
I ² C	inter-integrated circuit
IDE	integrated development environment
ILO	Internal Low-Speed Oscillator
IMO	Internal Main oscillator
INL	integral nonlinearity
I/O	input/output
IOR	I/O read
IOW	I/O write
IRES	initial power-on reset
IRA	interrupt request acknowledge
IRQ	interrupt request
ISR	interrupt service routine
IVR	interrupt vector read

Acronyms

Table 1 **Acronyms** (continued)

Symbol	Unit of measure
L2CAP	logical link control and adaptation protocol
LPCOMP	low-power comparator
LRb	last received bit
LRB	last received byte
LSb	least significant bit
LSB	least significant byte
LUT	lookup table
MISO	master-in-slave-out
MMIO	memory mapped input/output
MOSI	master-out-slave-in
MSb	most significant bit
MSB	most significant byte
PC	program counter
PCH	program counter high
PCL	program counter low
PD	power down
PGA	programmable gain amplifier
PM	power management
PMA	PSOC™ memory arbiter
POR	power-on reset
PPOR	precision power-on reset
PRS	pseudo random sequence
PSOC™	programmable system-on-chip
PSRR	power supply rejection ratio
PSSDC	power system sleep duty cycle
PWM	pulse width modulator
RAM	random-access memory
RETI	return from interrupt
RF	radio frequency
ROM	read only memory
RW	read/write
SAR	Successive Approximation register
SC	switched capacitor
SCB	Serial Communication Block
SIE	serial interface engine
SIO	special I/O
SE0	single-ended zero

Acronyms

Table 1 **Acronyms** (continued)

Symbol	Unit of measure
SNR	signal-to-noise ratio
SOF	start of frame
SOI	start of instruction
SP	stack pointer
SPD	sequential phase detector
SPI	serial peripheral interconnect
SPIM	serial peripheral interconnect master
SPIS	serial peripheral interconnect slave
SRAM	static random-access memory
SRSS	system resources sub-system
SROM	supervisory read only memory
SSADC	single slope ADC
SSC	supervisory system call
SYSCLK	system clock
SWD	single wire debug
TC	terminal count
TD	transaction descriptors
UART	Universal Asynchronous Receiver/Transmitter
UDB	universal digital block
USB	Universal Serial Bus
USBIO	USB I/O
WCO	watch crystal oscillator
WDT	watchdog timer
WDR	watchdog reset
XRES	external reset
XRES_N	external reset, active low

Supervisory Flash registers

1 Supervisory Flash registers

This section discusses the Supervisory Flash (SFLASH) registers. It lists all the registers in mapping tables, in address order.

1.1 Register details

Register	Address	Description
SFLASH_MSCLP_CLK_IMO_TRIM1_46	0x0FFFF08C	Local IMO Trim Register 1 for 46 MHz
SFLASH_MSCLP_CLK_IMO_TRIM2_46	0x0FFFF08D	Local IMO Trim Register 2 for 46MHz
SFLASH_MSCLP_CLK_IMO_TRIM3_46	0x0FFFF08E	Local IMO Trim Register 3 for 46MHz
SFLASH_MSCLP_CLK_IMO_TRIM1_38	0x0FFFF095	Local IMO Trim Register 1 for 38MHz
SFLASH_MSCLP_CLK_IMO_TRIM2_38	0x0FFFF096	Local IMO Trim Register 2 for 38MHz
SFLASH_MSCLP_CLK_IMO_TRIM3_38	0x0FFFF097	Local IMO Trim Register 3 for 38MHz
SFLASH_MSCLP_CLK_IMO_TRIM1_25	0x0FFFF09E	Local IMO Trim Register 1 for 25MHz
SFLASH_MSCLP_CLK_IMO_TRIM2_25	0x0FFFF09F	Local IMO Trim Register 2 for 25MHz
SFLASH_MSCLP_CLK_IMO_TRIM3_25	0x0FFFF0A0	Local IMO Trim Register 3 for 25MHz
SFLASH_SILICON_ID	0x0FFFF144	Silicon ID
SFLASH_HIB_KEY_DELAY	0x0FFFF150	Hibernate wakeup value for PWR_KEY_DELAY
SFLASH_DPSLP_KEY_DELAY	0x0FFFF152	Deep Sleep wakeup value for PWR_KEY_DELAY
SFLASH_SWD_CONFIG	0x0FFFF154	SWD pinout selector (not present in TSG4/TSG5-M)
SFLASH_SWD_LISTEN	0x0FFFF158	Listen Window Length
SFLASH_FLASH_START	0x0FFFF15C	Flash Image Start Address
SFLASH_IMO_TRIM_USBMODE_24	0x0FFFF1BE	USB IMO TRIM 24MHz
SFLASH_IMO_TRIM_USBMODE_48	0x0FFFF1BF	USB IMO TRIM 48MHz
SFLASH_IMO_TCTRIM_LT0	0x0FFFF1CC	IMO TempCo Trim Register (SRSS-Lite)
SFLASH_IMO_TCTRIM_LT1	0x0FFFF1CD	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT2	0x0FFFF1CE	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT3	0x0FFFF1CF	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT4	0x0FFFF1D0	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT5	0x0FFFF1D1	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT6	0x0FFFF1D2	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT7	0x0FFFF1D3	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT8	0x0FFFF1D4	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.

Supervisory Flash registers

Register	Address	Description
SFLASH_IMO_TCTRIM_LT9	0x0FFF1D5	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT10	0x0FFF1D6	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT11	0x0FFF1D7	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT12	0x0FFF1D8	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT13	0x0FFF1D9	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT14	0x0FFF1DA	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT15	0x0FFF1DB	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT16	0x0FFF1DC	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT17	0x0FFF1DD	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT18	0x0FFF1DE	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT19	0x0FFF1DF	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT20	0x0FFF1E0	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT21	0x0FFF1E1	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT22	0x0FFF1E2	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT23	0x0FFF1E3	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TCTRIM_LT24	0x0FFF1E4	IMO TempCo Trim Register (SRSS-Lite). See SFLASH_IMO_TCTRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT0	0x0FFF1E5	IMO Frequency Trim Register (SRSS-Lite)
SFLASH_IMO_TRIM_LT1	0x0FFF1E6	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT2	0x0FFF1E7	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT3	0x0FFF1E8	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT4	0x0FFF1E9	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT5	0x0FFF1EA	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.

Supervisory Flash registers

Register	Address	Description
SFLASH_IMO_TRIM_LT6	0x0FFF1EB	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT7	0x0FFF1EC	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT8	0x0FFF1ED	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT9	0x0FFF1EE	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT10	0x0FFF1EF	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT11	0x0FFF1F0	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT12	0x0FFF1F1	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT13	0x0FFF1F2	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT14	0x0FFF1F3	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT15	0x0FFF1F4	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT16	0x0FFF1F5	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT17	0x0FFF1F6	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT18	0x0FFF1F7	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT19	0x0FFF1F8	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT20	0x0FFF1F9	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT21	0x0FFF1FA	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT22	0x0FFF1FB	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT23	0x0FFF1FC	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.
SFLASH_IMO_TRIM_LT24	0x0FFF1FD	IMO Frequency Trim Register (SRSS-Lite). See SFLASH_IMO_TRIM_LT0 for the details of bit fields.

1.1.1 SFLASH_MSCLP_CLK_IMO_TRIM1_46

Local IMO Trim Register 1 for 46MHz

Address: 0x0FFFF08C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM1 [7:0]							

Bits	Name	Description
7 : 0	TRIM1	MSCLP IMO TRIM for 46 MHZ Default Value: X

1.1.2 SFLASH_MSCLP_CLK_IMO_TRIM2_46

Local IMO Trim Register 2 for 46MHz

Address: 0x0FFFF08D

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM2 [7:0]							

Bits	Name	Description
7 : 0	TRIM2	MSCLP IMO TRIM for 46 MHZ Default Value: X

1.1.3 SFLASH_MSCLP_CLK_IMO_TRIM3_46

Local IMO Trim Register 3 for 46MHz

Address: 0x0FFFF08E

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM3 [7:0]							

Bits	Name	Description
7 : 0	TRIM3	MSCLP IMO TRIM for 46 MHZ Default Value: X

1.1.4 SFLASH_MSCLP_CLK_IMO_TRIM1_38

Local IMO Trim Register 1 for 38MHz

Address: 0x0FFFF095

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM1 [7:0]							

Bits	Name	Description
7 : 0	TRIM1	MSCLP IMO TRIM for 38 MHZ Default Value: X

1.1.5 SFLASH_MSCLP_CLK_IMO_TRIM2_38

Local IMO Trim Register 2 for 38MHz

Address: 0x0FFFF096

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM2 [7:0]							

Bits	Name	Description
7 : 0	TRIM2	MSCLP IMO TRIM for 38 MHZ Default Value: X

1.1.6 SFLASH_MSCLP_CLK_IMO_TRIM3_38

Local IMO Trim Register 3 for 38MHz

Address: 0x0FFFF097

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM3 [7:0]							

Bits	Name	Description
7 : 0	TRIM3	MSCLP IMO TRIM for 38 MHZ Default Value: X

1.1.7 SFLASH_MSCLP_CLK_IMO_TRIM1_25

Local IMO Trim Register 1 for 25MHz

Address: 0x0FFFF09E

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM1 [7:0]							

Bits	Name	Description
7 : 0	TRIM1	MSCLP IMO TRIM for 25 MHZ Default Value: X

1.1.8 SFLASH_MSCLP_CLK_IMO_TRIM2_25

Local IMO Trim Register 2 for 25MHz

Address: 0x0FFFF09F

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM2 [7:0]							

Bits	Name	Description
7 : 0	TRIM2	MSCLP IMO TRIM for 25 MHZ Default Value: X

1.1.9 SFLASH_MSCLP_CLK_IMO_TRIM3_25

Local IMO Trim Register 3 for 25MHz

Address: 0x0FFFF0A0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM3 [7:0]							

Bits	Name	Description
7 : 0	TRIM3	MSCLP IMO TRIM for 25 MHZ Default Value: X

1.1.10 SFLASH_SILICON_ID

Silicon ID

Address: 0x0FFFF144

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	ID [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access								
Name	ID [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	ID	Silicon ID Default Value: X

1.1.11 SFLASH_HIB_KEY_DELAY

Hibernate wakeup value for PWR_KEY_DELAY

Address: 0x0FFFF150

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	WAKEUP_HOLDOFF [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	
HW Access	None						R	
Name	None [15:10]						WAKEUP_HOLDOFF [9:8]	

Bits	Name	Description
9 : 0	WAKEUP_HOLDOFF	Delay (in 12MHz IMO clock cycles) to wait for references to settle on wakeup from hibernate/ deepsleep. PBOD is ignored and system does not resume until this delay expires. Note that the same delay on POR is hard-coded. Default Value: X

1.1.12 SFLASH_DPSLP_KEY_DELAY

DeepSleep wakeup value for PWR_KEY_DELAY

Address: 0x0FFFF152

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	WAKEUP_HOLDOFF [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	
HW Access	None						R	
Name	None [15:10]						WAKEUP_HOLDOFF [9:8]	

Bits	Name	Description
9 : 0	WAKEUP_HOLDOFF	Delay (in 12MHz IMO clock cycles) to wait for references to settle on wakeup from hibernate/deepsleep. PBOD is ignored and system does not resume until this delay expires. Note that the same delay on POR is hard-coded. Default Value: X

1.1.13 SFLASH_SWD_CONFIG

SWD pinout selector (not present in TSG4/TSG5-M)

Address: 0x0FFFF154

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							
Name	None [7:1]							SWD_SELECT

Bits	Name	Description
0	SWD_SELECT	0: Use Primary SWD location 1: Use Alternate SWD location Default Value: X

1.1.14 SFLASH_SWD_LISTEN

Listen Window Length

Address: 0x0FFFF158

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	CYCLES [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access								
Name	CYCLES [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access								
Name	CYCLES [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access								
Name	CYCLES [31:24]							

Bits	Name	Description
31 : 0	CYCLES	Number of clock cycles Default Value: X

1.1.15 SFLASH_FLASH_START

Flash Image Start Address

Address: 0x0FFFF15C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	ADDRESS [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access								
Name	ADDRESS [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access								
Name	ADDRESS [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access								
Name	ADDRESS [31:24]							

Bits	Name	Description
31 : 0	ADDRESS	Start Address Default Value: X

1.1.16 SFLASH_IMO_TRIM_USBMODE_24

USB IMO TRIM 24MHz

Address: 0x0FFFF1BE

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM_24 [7:0]							

Bits	Name	Description
7 : 0	TRIM_24	TRIM value for IMO with USB at 24MHz Default Value: X

1.1.17 SFLASH_IMO_TRIM_USBMODE_48

USB IMO TRIM 48MHz

Address: 0x0FFFF1BF

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	TRIM_24 [7:0]							

Bits	Name	Description
7 : 0	TRIM_24	TRIM value for IMO with USB at 24MHz Default Value: X

1.1.18 SFLASH_IMO_TCTRIM_LT0

IMO TempCo Trim Register (SRSS-Lite)

Address: 0x0FFFF1CC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None	RW		RW				
HW Access	None	R		R				
Name	None	TCTRIM [6:5]		STEPsize [4:0]				

Bits	Name	Description
6 : 5	TCTRIM	IMO temperature compensation trim. These bits are determined at manufacturing time to adjust for temperature dependence. These bits are dependent on frequency and need to be changed using the Cypress provided frequency change algorithm. Default Value: 2
4 : 0	STEPsize	IMO trim stepsize bits. These bits are determined at manufacturing time to adjust for process variation. They are used to tune the stepsize of the FSOFFSET and OFFSET trims. Default Value: 16

1.1.19 SFLASH_IMO_TRIM_LT0

IMO Frequency Trim Register (SRSS-Lite)

Address: 0x0FFFF1E5

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	OFFSET [7:0]							

Bits	Name	Description
7 : 0	OFFSET	Frequency trim bits. These bits are determined at manufacturing time for each FREQ setting in CLK_IMO_SELECT and stored in SFLASH. The resultant values are loaded into CLK_IMO_TRIM1.OFFSET. Default Value: X

Peripheral registers

2 Peripheral registers

This section discusses the Peripheral registers. It lists all the registers in mapping tables, in address order.

2.1 Register details

Register	Address	Description
PERI_DIV_CMD	0x40010000	Divider command register
PERI_PCLK_CTL0	0x40010100	Programmable clock control register
PERI_PCLK_CTL1	0x40010104	Programmable clock control register. See PERI_PCLK_CTL0 for the details of bit fields.
PERI_PCLK_CTL2	0x40010108	Programmable clock control register. See PERI_PCLK_CTL0 for the details of bit fields.
PERI_PCLK_CTL3	0x4001010C	Programmable clock control register. See PERI_PCLK_CTL0 for the details of bit fields.
PERI_DIV_16_CTL0	0x40010300	Divider control register (for 16.0 divider)
PERI_DIV_16_CTL1	0x40010304	Divider control register (for 16.0 divider). See PERI_DIV_16_CTL0 for the details of bit fields.
PERI_DIV_16_5_CTL	0x40010400	Divider control register (for 16.5 divider)
PERI_DIV_24_5_CTL	0x40010500	Divider control register (for 24.5 divider)
PERI_TR_CTL	0x40010600	Trigger control register
PERI_TR_GROUP0_TR_OUT_CTL0	0x40012000	Trigger control register
PERI_TR_GROUP0_TR_OUT_CTL1	0x40012004	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.
PERI_TR_GROUP0_TR_OUT_CTL2	0x40012008	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.
PERI_TR_GROUP0_TR_OUT_CTL3	0x4001200C	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.
PERI_TR_GROUP0_TR_OUT_CTL4	0x40012010	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.
PERI_TR_GROUP0_TR_OUT_CTL5	0x40012014	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.
PERI_TR_GROUP0_TR_OUT_CTL6	0x40012018	Trigger control register. See PERI_TR_GROUP0_TR_OUT_CTL0 for the details of bit fields.

2.1.1 PERI_DIV_CMD

Divider command register

Address: 0x40010000

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW					
HW Access	R		R					
Name	SEL_TYPE [7:6]		SEL_DIV [5:0]					

Bits	15	14	13	12	11	10	9	8
SW Access	RW		RW					
HW Access	R		R					
Name	PA_SEL_TYPE [15:14]		PA_SEL_DIV [13:8]					

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	RW	None					
HW Access	RW1C	RW1C	None					
Name	ENABLE	DISABLE	None [29:24]					

Bits	Name	Description
31	ENABLE	Clock divider enable command (mutually exclusive with DISABLE). Typically, SW sets this field to '1' to enable a divider and HW sets this field to '0' to indicate that divider enabling has completed. When a divider is enabled, its integer and fractional (if present) counters are initialized to "0". If a divider is to be re-enabled using different integer and fractional divider values, the SW should follow these steps: 0: Disable the divider using the DIV_CMD.DISABLE field. 1: Configure the divider's DIV_XXX_CTL register. 2: Enable the divider using the DIV_CMD_ENABLE field. The SEL_DIV and SEL_TYPE fields specify which divider is to be enabled. The enabled divider may be phase aligned to either "clk_hf" (typical usage) or to ANY enabled divider. The PA_SEL_DIV and P_SEL_TYPE fields specify the reference divider. The HW sets the ENABLE field to '0' when the enabling is performed and the HW sets the DIV_XXX_CTL.EN field of the divider to '1' when the enabling is performed. Note that enabling with phase alignment to a low frequency divider takes time. E.g. To align to a divider that generates a clock of "clk_hf"/n (with n being the integer divider value INT_DIV+1), up to n cycles may be required to perform alignment. Phase alignment to "clk_hf" takes affect immediately. SW can set this field to '0' during phase alignment to abort the enabling process. Default Value: 0

2.1.1 PERI_DIV_CMD (continued)

30	DISABLE	Clock divider disable command (mutually exclusive with ENABLE). SW sets this field to '1' and HW sets this field to '0'. The SEL_DIV and SEL_TYPE fields specify which divider is to be disabled. The HW sets the DISABLE field to '0' immediately and the HW sets the DIV_XXX_CTL.EN field of the divider to '0' immediately. Default Value: 0
15 : 14	PA_SEL_TYPE	Specifies the divider type of the divider to which phase alignment is performed for the clock enable command: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers. Default Value: 3
13 : 8	PA_SEL_DIV	(PA_SEL_TYPE, PA_SEL_DIV) specifies the divider to which phase alignment is performed for the clock enable command. Any enabled divider can be used as reference. This allows all dividers to be aligned with each other, even when they are enabled at different times. If PA_SEL_DIV is "63" and "PA_SEL_TYPE" is "3", "clk_hf" is used as reference. Default Value: 63
7 : 6	SEL_TYPE	Specifies the divider type of the divider on which the command is performed: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers. Default Value: 3
5 : 0	SEL_DIV	(SEL_TYPE, SEL_DIV) specifies the divider on which the command (DISABLE/ENABLE) is performed. If SEL_DIV is "63" and "SEL_TYPE" is "3" (default/reset value), no divider is specified and no clock signal(s) are generated. Default Value: 63

2.1.2 PERI_PCLK_CTL0

Programmable clock control register

Address: 0x40010100

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		None					RW
HW Access	R		None					R
Name	SEL_TYPE [7:6]		None [5:1]					SEL_DIV

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 6	SEL_TYPE	Specifies divider type: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers. Default Value: 3
0	SEL_DIV	Specifies one of the dividers of the divider type specified by SEL_TYPE. If SEL_DIV is "63" and "SEL_TYPE" is "3" (default/reset value), no divider is specified and no clock control signal(s) are generated. When transitioning a clock between two out of phase dividers, spurious clock control signals may be generated for one "clk_hf" cycle during this transition. These clock control signals may cause a single clock period that is smaller than any of the two divider periods. To prevent these spurious clock signals, the clock multiplexer can be disconnected (SEL_DIV is "63" and "SEL_TYPE" is "3") for a transition time that is larger than the smaller of the two divider periods. Default Value: 1

2.1.3 PERI_DIV_16_CTL0

Divider control register (for 16.0 divider)

Address: 0x40010300

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							R
HW Access	None							RW
Name	None [7:1]							EN

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	INT16_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	INT16_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 8	INT16_DIV	Integer division by (1+INT16_DIV). Allows for integer divisions in the range [1, 65,536]. Note: this type of divider does NOT allow for a fractional division. For the generation of a divided clock, the integer division range is restricted to [2, 65,536]. for the generation of a 50/50% duty cycle digital divided clock, the integer division range is restricted to even numbers in the range [2, 65,536]. The generation of a 50/50 % duty cycle analog divided clock has no restrictions. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to "0" when transitioning from DeepSleep to Active power mode. Default Value: 0
0	EN	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result of a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode. Default Value: 0

2.1.4 PERI_DIV_16_5_CTL

Divider control register (For 16.5 divider)

Address: 0x40010400

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW					None		R
HW Access	R					None		RW
Name	FRAC5_DIV [7:3]					None [2:1]		EN

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	INT16_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	INT16_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 8	INT16_DIV	Integer division by (1+INT16_DIV). Allows for integer divisions in the range [1, 65,536]. Note: combined with fractional division, this divider type allows for a division in the range [1, 65,536 31/32] in 1/32 increments. For the generation of a divided clock, the division range is restricted to [2, 65,536 31/32]. For the generation of a 50/50% duty cycle divided clock, the division range is restricted to [2, 65,536]. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to "0" when transitioning from DeepSleep to Active power mode. Default Value: 0
7 : 3	FRAC5_DIV	Fractional division by (FRAC5_DIV/32). Allows for fractional divisions in the range [0, 31/32]. Note that fractional division results in clock jitter as some clock periods may be 1 "clk_hf" cycle longer than other clock periods. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to "0" when transitioning from DeepSleep to Active power mode. Default Value: 0
0	EN	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result on a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode. Default Value: 0

2.1.5 PERI_DIV_24_5_CTL

Divider control register (For 24.5 divider)

Address: 0x40010500

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW					None		R
HW Access	R					None		RW
Name	FRAC5_DIV [7:3]					None [2:1]		EN

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	INT24_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	INT24_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access	R							
Name	INT24_DIV [31:24]							

Bits	Name	Description
31 : 8	INT24_DIV	Integer division by (1+INT24_DIV). Allows for integer divisions in the range [1, 16,777,216]. Note: combined with fractional division, this divider type allows for a division in the range [1, 16,777,216 31/32] in 1/32 increments. For the generation of a divided clock, the integer division range is restricted to [2, 16,777,216 31/32]. For the generation of a 50/50% duty cycle divided clock, the division range is restricted to [2, 16,777,216]. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to "0" when transitioning from DeepSleep to Active power mode. Default Value: 0
7 : 3	FRAC5_DIV	Fractional division by (FRAC5_DIV/32). Allows for fractional divisions in the range [0, 31/32]. Note that fractional division results in clock jitter as some clock periods may be 1 "clk_hf" cycle longer than other clock periods. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to "0" when transitioning from DeepSleep to Active power mode. Default Value: 0
0	EN	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result on a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode. Default Value: 0

2.1.6 PERI_TR_CTL

Trigger control register

Address: 0x40010600

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None	RW						
HW Access	None	R						
Name	None	TR_SEL [6:0]						

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW			
HW Access	None				R			
Name	None [15:12]				TR_GROUP [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	RW							
Name	TR_COUNT [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	RW	None					
HW Access	RW1C	R	None					
Name	TR_ACT	TR_OUT	None [29:24]					

Bits	Name	Description
31	TR_ACT	SW sets this field to '1' to activate (set to '1') a trigger as identified by TR_SEL and TR_OUT for TR_COUNT cycles. HW sets this field to '0' when the cycle counter is decremented to "0". Note: a TR_COUNT value of 255 is a special case and trigger activation is under direct control of the TR_ACT field (the counter is not decremented). Note: when TR_ACT is '1', SW should not modify the other register fields. SW MUST NOT set TR_ACT bit to '1' while updating the other register bits simultaneously. At first the SW MUST update the other register bits as needed, and then set TR_ACT to '1' with a new register write." Default Value: 0
30	TR_OUT	Specifies whether trigger activation is for a specific input or output trigger of the trigger multiplexer. Activation of a specific input trigger, will result in activation of all output triggers that have the specific input trigger selected through their TR_OUT_CTL.SEL field. Activation of a specific output trigger, will result in activation of the specified TR_SEL output trigger only. '0': TR_SEL selection and trigger activation is for an input trigger to the trigger multiplexer. '1': TR_SEL selection and trigger activation is for an output trigger from the trigger multiplexer. Default Value: 0
23 : 16	TR_COUNT	Amount of cycles a specific trigger is activated. During activation (TR_ACT is '1'), HW decrements this field to "0" using a cycle counter. During activation, SW should not modify this register field. A value of 255 is a special case: HW does NOT decrement this field to "0" and trigger activation is under direct control of TR_ACT: when TR_ACT is '1' the trigger is activated and when TR_ACT is '0' the trigger is deactivated. Default Value: 0
11 : 8	TR_GROUP	Specifies the trigger group. Default Value: 0

2.1.6 PERI_TR_CTL (continued)

6 : 0	TR_SEL	Specifies the activated trigger when TR_ACT is '1'. TR_OUT specifies whether the activated trigger is an input trigger or output trigger to the trigger multiplexer. During activation (TR_ACT is '1'), SW should not modify this register field. If the specified trigger is not present, the trigger activation has no effect. Default Value: 0
-------	--------	---

2.1.7 PERI_TR_GROUP0_TR_OUT_CTL0

Trigger control register

Address: 0x40012000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3 : 0	SEL	Specifies input trigger. This field is typically set during the setup of a chip use case scenario. Changing this field while activated triggers are present on the input triggers may result in unpredictable behavior. Note that input trigger 0 (default value) is typically connected to a constant signal level of '0', and as a result will not cause HW activation of the output trigger. Default Value: 0

High Speed IO Matrix (HSIOM) registers

3 High Speed IO Matrix (HSIOM) registers

This section discusses the HSIOM registers. It lists all the registers in mapping tables, in address order.

3.1 Register details

Register	Address	Description
HSIOM_PORT_SEL0	0x40020000	Port selection register
HSIOM_PORT_SEL1	0x40020100	Port selection register
HSIOM_PORT_SEL2	0x40020200	Port selection register. See HSIOM_PORT_SEL0 for the details of bit fields.
HSIOM_PORT_SEL3	0x40020300	Port selection register
HSIOM_PORT_SEL4	0x40020400	Port selection register. See HSIOM_PORT_SEL3 for the details of bit fields.

3.1.1 HSIOM_PORT_SEL0

Port selection register

Address: 0x40020000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	RW				RW			
Name	IO1_SEL [7:4]				IO0_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	RW				RW			
HW Access	RW				RW			
Name	IO3_SEL [15:12]				IO2_SEL [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	RW				RW			
HW Access	RW				RW			
Name	IO5_SEL [23:20]				IO4_SEL [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 20	IO5_SEL	Selects connection for IO pad 5 route. Default Value: 0
19 : 16	IO4_SEL	Selects connection for IO pad 4 route. Default Value: 0
15 : 12	IO3_SEL	Selects connection for IO pad 3 route. Default Value: 0
11 : 8	IO2_SEL	Selects connection for IO pad 2 route. Default Value: 0
7 : 4	IO1_SEL	Selects connection for IO pad 1 route. Default Value: 0
3 : 0	IO0_SEL	Selects connection for IO pad 0 route. Default Value: 0

0x0: GPIO :

SW controlled GPIO.

0x1: GPIO_DSI :

SW controlled "out", DSI controlled "oe_n".

3.1.1 HSIOM_PORT_SEL0 (continued)

0x2: DSI_DSI :

DSI controlled "out" and "oe_n".

0x3: DSI_GPIO :

DSI controlled "out", SW controlled "oe_n".

0x4: CSD_SENSE :

CapSense sense connection (analog mode)

0x5: CSD_SHIELD :

CapSense shield connection (analog mode)

0x6: AMUXA :

AMUXBUS A connection.

0x7: AMUXB :

AMUXBUS B connection.

0x8: ACT_0 :

Chip specific Active source 0 connection.

0x9: ACT_1 :

Chip specific Active source 1 connection.

0xa: ACT_2 :

Chip specific Active source 2 connection.

0xb: ACT_3 :

Chip specific Active source 3 connection.

0xc: LCD_COM :

LCD common connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xd: LCD_SEG :

LCD segment connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xc: DS_0 :

Chip specific DeepSleep source 0 connection.

0xd: DS_1 :

Chip specific DeepSleep source 1 connection.

3.1.1 HSIOM_PORT_SEL0 (continued)

0xe: DS_2 :

Chip specific DeepSleep source 2 connection.

0xf: DS_3 :

Chip specific DeepSleep source 3 connection.

3.1.2 HSIOM_PORT_SEL1

Port selection register

Address: 0x40020100

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				RW			
Name	None [7:4]				IO0_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3 : 0	IO0_SEL	Selects connection for IO pad 0 route. Default Value: 0 0x0: GPIO : SW controlled GPIO. 0x1: GPIO_DSI : SW controlled "out", DSI controlled "oe_n". 0x2: DSI_DSI : DSI controlled "out" and "oe_n". 0x3: DSI_GPIO : DSI controlled "out", SW controlled "oe_n". 0x4: CSD_SENSE : CapSense sense connection (analog mode)

3.1.2 HSIOM_PORT_SEL1 (continued)

0x5: CSD_SHIELD :

CapSense shield connection (analog mode)

0x6: AMUXA :

AMUXBUS A connection.

0x7: AMUXB :

AMUXBUS B connection.

0x8: ACT_0 :

Chip specific Active source 0 connection.

0x9: ACT_1 :

Chip specific Active source 1 connection.

0xa: ACT_2 :

Chip specific Active source 2 connection.

0xb: ACT_3 :

Chip specific Active source 3 connection.

0xc: LCD_COM :

LCD common connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xd: LCD_SEG :

LCD segment connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xc: DS_0 :

Chip specific DeepSleep source 0 connection.

0xd: DS_1 :

Chip specific DeepSleep source 1 connection.

0xe: DS_2 :

Chip specific DeepSleep source 2 connection.

0xf: DS_3 :

Chip specific DeepSleep source 3 connection.

3.1.3 HSIOM_PORT_SEL3

Port selection register

Address: 0x40020300

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	RW				RW			
Name	IO1_SEL [7:4]				IO0_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	RW				RW			
HW Access	RW				RW			
Name	IO3_SEL [15:12]				IO2_SEL [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 12	IO3_SEL	Selects connection for IO pad 3 route. Default Value: 0
11 : 8	IO2_SEL	Selects connection for IO pad 2 route. Default Value: 0
7 : 4	IO1_SEL	Selects connection for IO pad 1 route. Default Value: 0
3 : 0	IO0_SEL	Selects connection for IO pad 0 route. Default Value: 0

0x0: GPIO :

SW controlled GPIO.

0x1: GPIO_DSI :

SW controlled "out", DSI controlled "oe_n".

0x2: DSI_DSI :

DSI controlled "out" and "oe_n".

0x3: DSI_GPIO :

DSI controlled "out", SW controlled "oe_n".

3.1.3 HSIOM_PORT_SEL3 (continued)

0x4: CSD_SENSE :

CapSense sense connection (analog mode)

0x5: CSD_SHIELD :

CapSense shield connection (analog mode)

0x6: AMUXA :

AMUXBUS A connection.

0x7: AMUXB :

AMUXBUS B connection.

0x8: ACT_0 :

Chip specific Active source 0 connection.

0x9: ACT_1 :

Chip specific Active source 1 connection.

0xa: ACT_2 :

Chip specific Active source 2 connection.

0xb: ACT_3 :

Chip specific Active source 3 connection.

0xc: LCD_COM :

LCD common connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xd: LCD_SEG :

LCD segment connection. This mode provides DeepSleep functionality (provided that the LCD block exists, is enabled and is properly configured).

0xc: DS_0 :

Chip specific DeepSleep source 0 connection.

0xd: DS_1 :

Chip specific DeepSleep source 1 connection.

0xe: DS_2 :

Chip specific DeepSleep source 2 connection.

0xf: DS_3 :

Chip specific DeepSleep source 3 connection.

System Resources Subsystem (SRSS) registers

4 System Resources Subsystem (SRSS) registers

This section discusses the SRSSLT registers. It lists all the registers in mapping tables, in address order.

4.1 Register details

Register	Address	Description
PWR_CONTROL	0x40030000	Power Mode Control
PWR_KEY_DELAY	0x40030004	Power System Key&Delay Register
PWR_DDFT_SELECT	0x4003000C	Power DDFT Mode Selection Register
TST_MODE	0x40030014	Test Mode Control Register
CLK_SELECT	0x40030028	Clock Select Register
CLK_ILO_CONFIG	0x4003002C	ILO Configuration
CLK_IMO_CONFIG	0x40030030	IMO Configuration
CLK_DFT_SELECT	0x40030034	Clock DFT Mode Selection Register
WDT_DISABLE_KEY	0x40030038	Watchdog Disable Key Register
WDT_COUNTER	0x4003003C	Watchdog Counter Register
WDT_MATCH	0x40030040	Watchdog Match Register
SRSS_INTR	0x40030044	SRSS Interrupt Register
SRSS_INTR_SET	0x40030048	SRSS Interrupt Set Register
SRSS_INTR_MASK	0x4003004C	SRSS Interrupt Mask Register
RES_CAUSE	0x40030054	Reset Cause Observation Register
CLK_IMO_SELECT	0x40030F08	IMO Frequency Select Register
CLK_IMO_TRIM1	0x40030F0C	IMO Trim Register
CLK_IMO_TRIM2	0x40030F10	IMO Trim Register
PWR_PWRSYS_TRIM1	0x40030F14	Power System Trim Register
CLK_IMO_TRIM3	0x40030F18	IMO Trim Register

4.1.1 PWR_CONTROL

Power Mode Control

Address: 0x40030000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		R	R	R			
HW Access	None		RW	RW	RW			
Name	None [7:6]		LP- M_READY	DEBUG_- SESSION	POWER_MODE [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW	None			R		RW	RW
HW Access	A	None			RW		R	R
Name	EXT_VCCD	None [22:20]			SPARE [19:18]		OVER_- TEMP_- THRESH	OVER_- TEMP_EN

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23	EXT_VCCD	Always write 0. Default Value: 0
19 : 18	SPARE	Spare AHB readback bits that are hooked to PWR_PWRSYS_TRIM1.SPARE_TRIM[1:0] through spare logic equivalent to bitwise inversion. Engineering only. Default Value: 0
17	OVER_TEMP_THRESH	Over-temperature threshold. 0: TEMP_HIGH condition occurs between 120C and 125C. 1: TEMP_HIGH condition occurs between 60C and 75C (used for testing). Default Value: 0
16	OVER_TEMP_EN	Enable the die over temperature sensor. Must be enabled when using the TEMP_HIGH interrupt. 0: Disable 1: Enable Default Value: 0
5	LPM_READY	Indicates whether the low power mode regulator is ready to enter DEEPSLEEP mode. 0: If DEEPSLEEP mode is requested, device will enter SLEEP mode. When low power regulators are ready, device will automatically enter the originally requested mode. 1: Normal operation. DEEPSLEEP works as described. Default Value: 0
4	DEBUG_SESSION	Indicates whether a debug session is active 0: Inactive 1: Active Default Value: 0

4.1.1 PWR_CONTROL (continued)

0x0: NO_SESSION :

No debug session active

0x1: SESSION_ACTIVE :

Debug session is active

3 : 0 POWER_MODE

Current power mode of the device. Note that this field cannot be read in all power modes on actual silicon.
Default Value: 0

0x0: RESET :

RESET state

0x1: ACTIVE :

ACTIVE state

0x2: SLEEP :

SLEEP state

0x3: DEEP_SLEEP :

DEEP_SLEEP state

4.1.2 PWR_KEY_DELAY

Power System Key Register

Address: 0x40030004

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	WAKEUP_HOLDOFF [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	
HW Access	None						R	
Name	None [15:10]						WAKEUP_HOLDOFF [9:8]	

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9 : 0	WAKEUP_HOLDOFF	Delay to wait for references to settle on wakeup from deepsleep. BOD is ignored and system does not resume until this delay expires. Note that the same delay on POR is hard-coded. The default assumes the output of the predivider is 48MHz + 3%. Firmware may scale this setting according to the fastest actual clock frequency that can occur when waking from DEEPSLEEP. Default Value: 248

4.1.3 PWR_DDFT_SELECT

Power DDFT Mode Selection Register

Address: 0x4003000C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	R				R			
Name	DDFT1_SEL [7:4]				DDFT0_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	DDFT1_SEL	Select signal for power DDFT output #1 Default Value: 0
		0x0: WAKEUP :
		wakeup
		0x1: AWAKE :
		awake
		0x2: ACT_POWER_EN :
		act_power_en
		0x3: ACT_POWER_UP :
		act_power_up
		0x4: ACT_POWER_GOOD :
		act_power_good

4.1.3 PWR_DDFT_SELECT (continued)

0x5: ACT_REF_VALID :

act_ref_valid

0x6: ACT_REG_VALID :

act_reg_valid

0x7: ACT_COMP_OUT :

act_comp_out

0x8: ACT_TEMP_HIGH :

act_temp_high

0x9: DPSLP_COMP_OUT :

dpslp_comp_out

0xa: DPSLP_POWER_UP :

dpslp_power_up

0xb: AWAKE_DELAYED :

awake_delayed

0xc: LPM_READY :

lpm_ready

0xd: SLEEPHOLDACK_N :

sleepholdack_n

0xe: GND :

1'b0

0xf: PWR :

1'b1

3 : 0 DDFT0_SEL Select signal for power DDFT output #0
Default Value: 0

0x0: WAKEUP :

wakeup

0x1: AWAKE :

awake

4.1.3 PWR_DDFT_SELECT (continued)

0x2: ACT_POWER_EN :

act_power_en

0x3: ACT_POWER_UP :

act_power_up

0x4: ACT_POWER_GOOD :

act_power_good

0x5: ACT_REF_EN :

srss_adft_control_act_ref_en

0x6: ACT_COMP_EN :

srss_adft_control_act_comp_en

0x7: DPSLP_REF_EN :

srss_adft_control_dpslp_ref_en

0x8: DPSLP_REG_EN :

srss_adft_control_dpslp_reg_en

0x9: DPSLP_COMP_EN :

srss_adft_control_dpslp_comp_en

0xa: OVER_TEMP_EN :

pwr_control_over_temp_en

0xb: SLEEPHOLDREQ_N :

sleepholdreq_n

0xc: ADFT_BUF_EN :

adft_buf_en

0xd: ATPG_OBSERVE :

ATPG observe point (no functional purpose)

0xe: GND :

1'b0

0xf: PWR :

1'b1

4.1.4 TST_MODE

Test Mode Control Register

Address: 0x40030014

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					R	None	
HW Access	None					RW	None	
Name	None [7:3]					SWD_CONNECTED	None	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	R	None	RW	None			
HW Access	R	RW	None	A	None			
Name	TEST_MODE	TEST_KEY_DFT_EN	None	BLOCK_AL T_XRES	None [27:24]			

Bits	Name	Description
31	TEST_MODE	Setting this bit will prevent BootROM from yielding execution to Flash image. 0: Normal operation mode 1: Test mode (any test mode) Default Value: 0
30	TEST_KEY_DFT_EN	This bit is set when a XRES test mode key is shifted in. It is the value of the test_key_dft_en signal. When this bit is set, the BootROM will not yield execution to the FLASH image (same function as setting TEST_MODE bit below). Default Value: 0
28	BLOCK_ALT_XRES	Relevant only for parts that have the alternate XRES mechanism of overloading a GPIO pin temporarily as alternate XRES during test. When set, this bit blocks the alternate XRES function, such that the pin can be used for normal I/O or for ddf/adt observation. This register bit only resets for XRES, POR, or a detected BOD. Default Value: 0
2	SWD_CONNECTED	Indicates SWD Connection status 0: SWD not active 1: SWD activated (Line Reset & Connect sequence passed) Default Value: 0

4.1.5 CLK_SELECT

Clock Select Register

Address: 0x40030028

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW		RW		RW	
HW Access	R		R		R		R	
Name	SYSCLK_DIV [7:6]		PUMP_SEL [5:4]		HFCLK_DIV [3:2]		HFCLK_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 6	SYSCLK_DIV	Select clk_sys prescaler value. Default Value: 0 0x0: NO_DIV : clk_sys= clk_hf/1 0x1: DIV_BY_2 : clk_sys= clk_hf/2 0x2: DIV_BY_4 : clk_sys= clk_hf/4 0x3: DIV_BY_8 : clk_sys= clk_hf/8
5 : 4	PUMP_SEL	Selects clock source for charge pump clock. This clock is not guaranteed to be glitch free when changing any of its sources or settings. Default Value: 0 0x0: GND : No clock, connect to gnd

4.1.5 CLK_SELECT (continued)

0x1: IMO :

Use main IMO output

0x2: HFCLK :

Use clk_hf (using selected source after predivider but before prescaler)

3 : 2 HFCLK_DIV

Selects clk_hf predivider value.
Default Value: 2

0x0: NO_DIV :

Transparent mode, feed through selected clock source w/o dividing.

0x1: DIV_BY_2 :

Divide selected clock source by 2

0x2: DIV_BY_4 :

Divide selected clock source by 4

0x3: DIV_BY_8 :

Divide selected clock source by 8

1 : 0 HFCLK_SEL

Selects a source for clk_hf and dsi_in[0]. Note that not all products support all clock sources. Selecting a clock source that is not supported will result in undefined behavior.
Default Value: 0

0x0: IMO :

IMO - Internal R/C Oscillator

0x1: EXTCLK :

EXTCLK - External Clock Pin

0x2: ECO :

ECO - External-Crystal Oscillator or PLL subsystem output

4.1.6 CLK_ILO_CONFIG

ILO Configuration

Address: 0x4003002C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	None						
HW Access	RW	None						
Name	ENABLE	None						

Bits	Name	Description
31	ENABLE	Master enable for ILO oscillator. This bit is hardware set whenever the WDT_DISABLE_KEY is not set to the magic value. Default Value: 1

4.1.7 CLK_IMO_CONFIG

IMO Configuration

Address: 0x40030030

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	None						
HW Access	R	None						
Name	ENABLE	None						

Bits	Name	Description
31	ENABLE	Master enable for IMO oscillator. Clearing this bit will disable the IMO. Don't do this if the system is running off it. Default Value: 1

4.1.8 CLK_DFT_SELECT

Clock DFT Mode Selection Register

Address: 0x40030034

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None	RW	RW		RW			
HW Access	None	R	R		R			
Name	None	DFT_EDGE 0	DFT_DIV0 [5:4]		DFT_SEL0 [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None	RW	RW		RW			
HW Access	None	R	R		R			
Name	None	DFT_EDGE 1	DFT_DIV1 [13:12]		DFT_SEL1 [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
14	DFT_EDGE1	Edge sensitivity for in-line divider on output #1 (only relevant when DIV1>0). Default Value: 0 0x0: POSEDGE : Use posedge for divider 0x1: NEGEDGE : Use negedge for divider
13 : 12	DFT_DIV1	DFT Output Divide Down. Default Value: 0 0x0: NO_DIV : Direct Output 0x1: DIV_BY_2 : Divide by 2

4.1.8 CLK_DFT_SELECT (continued)

		0x2: DIV_BY_4 :
		Divide by 4
		0x3: DIV_BY_8 :
		Divide by 8
11 : 8	DFT_SEL1	Select signal for DFT output #1 Default Value: 0
		0x0: NC :
		Disabled - output is 0
		0x1: ILO :
		clk_ilo: ILO output
		0x2: IMO :
		clk_imo: IMO primary output
		0x3: ECO :
		clk_eco: ECO output
		0x4: EXTCLK :
		clk_ext: external clock input
		0x5: HFCLK :
		clk_hf: root of the high-speed clock tree
		0x6: LFCLK :
		clk_lf: root of the low-speed clock tree
		0x7: SYSCCLK :
		clk_sys: root of the CPU/AHB clock tree (gated version of clk_hf)
		0x8: PUMPCLK :
		clk_pump: clock provided to charge pumps in FLASH and PA
		0x9: SLPCTRLCLK :
		clk_slpctrl: clock provided to SleepController
6	DFT_EDGE0	Edge sensitivity for in-line divider on output #0 (only relevant when DIV0>0). Default Value: 0
		0x0: POSEDGE :
		Use posedge for divider

4.1.8 CLK_DFT_SELECT (continued)

0x1: NEGEDGE :

Use negedge for divider

5 : 4 DFT_DIV0

DFT Output Divide Down.
Default Value: 0

0x0: NO_DIV :

Direct Output

0x1: DIV_BY_2 :

Divide by 2

0x2: DIV_BY_4 :

Divide by 4

0x3: DIV_BY_8 :

Divide by 8

3 : 0 DFT_SELO

Select signal for DFT output #0
Default Value: 0

0x0: NC :

Disabled - output is 0

0x1: ILO :

clk_ilo: ILO output

0x2: IMO :

clk_imo: IMO primary output

0x3: ECO :

clk_eco: ECO output

0x4: EXTCLK :

clk_ext: external clock input

0x5: HFCLK :

clk_hf: root of the high-speed clock tree

0x6: LFCLK :

clk_lf: root of the low-speed clock tree

0x7: SYSCCLK :

clk_sys: root of the CPU/AHB clock tree (gated version of clk_hf)

4.1.8 CLK_DFT_SELECT (continued)

0x8: PUMPCLK :

clk_pump: clock provided to charge pumps in FLASH and PA

0x9: SLPCTRLCLK :

clk_slpctrl: clock provided to SleepController

4.1.9 WDT_DISABLE_KEY

Watchdog Disable Key Register

Address: 0x40030038

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	KEY [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	KEY [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	KEY [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access	R							
Name	KEY [31:24]							

Bits	Name	Description
31 : 0	KEY	Disables WDT reset when equal to 0xACED8865. The WDT reset functions normally for any other setting. Default Value: 0

4.1.10 WDT_COUNTER

Watchdog Counter Register

Address: 0x4003003C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	RW							
Name	COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	RW							
Name	COUNTER [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	COUNTER	Current value of WDT Counter Default Value: 0

4.1.11 WDT_MATCH

Watchdog Match Register

Address: 0x40030040

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	MATCH [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	MATCH [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None				RW			
HW Access	None				R			
Name	None [23:20]				IGNORE_BITS [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
19 : 16	IGNORE_BITS	The number of MSB bits of the watchdog timer that are NOT checked against MATCH. This value provides control over the time-to-reset of the watchdog (which happens after 3 successive matches). Note that certain products may enforce a minimum value for this register through design time configuration. Default Value: 0
15 : 0	MATCH	Match value for Watchdog counter. Every time WDT_COUNTER reaches MATCH an interrupt is generated. Two unserviced interrupts will lead to a system reset (i.e. at the third match). Default Value: 4096

4.1.12 SRSS_INTR

SRSS Interrupt Register

Address: 0x40030044

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW1C	RW1C
HW Access	None						A	A
Name	None [7:2]						TEMP_HIGH	WDT_MATCH

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	TEMP_HIGH	Regulator over-temp interrupt. This interrupt can occur when a short circuit exists on the vccd pin or when extreme loads are applied on IO-cells causing the die to overheat. Firmware is encouraged to shutdown all IO cells and then go to DeepSleep mode when this interrupt occurs if protection against such conditions is desired. Default Value: 0
0	WDT_MATCH	WDT Interrupt Request. This bit is set each time WDT_COUNTER==WDT_MATCH. Clearing this bit also feeds the watch dog. Missing 2 interrupts in a row will generate brown-out reset. Due to internal synchronization, it takes 2 SYSCLK cycles to update after a W1C. Default Value: 0

4.1.13 SRSS_INTR_SET

SRSS Interrupt Set Register

Address: 0x40030048

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW1S	None
HW Access	None						A	None
Name	None [7:2]						TEMP_HIGH	None

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	TEMP_HIGH	Writing 1 to this bit internally sets the overtemp interrupt. This can be observed by reading SRSS_INTR.TEMP_HIGH. This bit always reads back as zero. Default Value: 0

4.1.14 SRSS_INTR_MASK

SRSS Interrupt Mask Register

Address: 0x4003004C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [7:2]						TEMP_HIGH	WDT_MATCH

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	TEMP_HIGH	Masks REG_OVERTEMP interrupt Default Value: 0
0	WDT_MATCH	Clearing this bit will not forward the interrupt to the CPU. It will not, however, disable the WDT reset generation on 2 missed interrupts. Default Value: 0

4.1.15 RES_CAUSE

Reset Cause Observation Register

Address: 0x40030054

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW1C	RW1C	None		RW1C
HW Access	None			A	A	None		A
Name	None [7:5]			RESET_ SOFT	RE- SET_PROT _FAULT	None [2:1]		RE- SET_WDT

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
4	RESET_SOFT	Cortex-M0 requested a system reset through it's SYSRESETREQ. This can be done via a debugger probe or in firmware. Default Value: 0
3	RESET_PROT_FAULT	A protection violation occurred that requires a RESET. This includes, but is not limited to, hitting a debug breakpoint while in Privileged Mode. Default Value: 0
0	RESET_WDT	A WatchDog Timer reset has occurred since last power cycle. Default Value: 0

4.1.16 CLK_IMO_SELECT

IMO Frequency Select Register

Address: 0x40030F08

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW		
HW Access	None					R		
Name	None [7:3]					FREQ [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
2 : 0	FREQ	Select operating frequency Default Value: 0 0x0: 24_MHZ : IMO runs at 24 MHz 0x1: 28_MHZ : IMO runs at 28 MHz 0x2: 32_MHZ : IMO runs at 32 MHz 0x3: 36_MHZ : IMO runs at 36 MHz 0x4: 40_MHZ : IMO runs at 40 MHz

4.1.16 CLK_IMO_SELECT (continued)

0x5: 44_MHZ :

IMO runs at 44 MHz

0x6: 48_MHZ :

IMO runs at 48 MHz

4.1.17 CLK_IMO_TRIM1

IMO Trim Register

Address: 0x40030F0C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	OFFSET [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	OFFSET	Frequency trim bits. These bits are determined at manufacturing time for each FREQ setting in CLK_IMO_SELECT and stored in SFLASH. For devices that have either USB or a WCO, this field is hardware updated during USB osclock mode or when a WCO uses this mechanism for PLL locking the WCO. This field is mapped to the most significant bits of the IMO trim imo_clk_trim[10:3]. The step size of 1 LSB on this field is approximately 120 kHz. Default Value: 128

4.1.18 CLK_IMO_TRIM2

IMO Trim Register

Address: 0x40030F10

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW		
HW Access	None					RW		
Name	None [7:3]					FSOFFSET [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
2 : 0	FSOFFSET	Frequency trim bits. These bits are not trimmed during manufacturing and kept at 0 under normal operation. This field is hardware updated during USB osclock mode or when a WCO uses this mechanism for PLL locking the WCO. This is only available with devices that have either USB or a WCO. . This field is mapped to the least significant bits of the IMO trim imo_clk_trim[2:0]. The step size of 1 LSB on this field is approximately 15 kHz. Default Value: 0

4.1.19 PWR_PWRSYS_TRIM1

Power System Trim Register

Address: 0x40030F14

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	R				R			
Name	SPARE_TRIM [7:4]				DPSLP_REF_TRIM [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	SPARE_TRIM	Active-Reference temperature compensation trim (repurposed from spare bits). Bits [7:6] - trim the Active-Reference IREF temperature coefficient (TC). 00: TC = 0 (unchanged) 01: TC = +80ppm/C 10: TC = -80ppm/C 11: TC = -150ppm/C Bits [5:4] - trim the Active-Reference VREF temperature coefficient (TC). 00: TC = 0 (unchanged) 01: TC = -50ppm/C 10: TC = -80ppm/C 11: TC = +150ppm/C Default Value: 0
3 : 0	DPSLP_REF_TRIM	Trims the DeepSleep reference that is used by the DeepSleep regulator and DeepSleep power comparator. Default Value: 0

4.1.20 CLK_IMO_TRIM3

IMO Trim Register

Address: 0x40030F18

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None	RW		RW				
HW Access	None	R		R				
Name	None	TCTRIM [6:5]		STEPSIZE [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
6 : 5	TCTRIM	IMO temperature compensation trim. These bits are determined at manufacturing time to adjust for temperature dependence. These bits are dependent on frequency and need to be changed using the Cypress provided frequency change algorithm. Default Value: 2
4 : 0	STEPSIZE	IMO trim stepsize bits. These bits are determined at manufacturing time to adjust for process variation. They are used to tune the stepsize of the FSOFFSET and OFFSET trims. Default Value: 16

General Purpose IO (GPIO) registers

5 General Purpose IO (GPIO) registers

This section discusses the GPIO registers. It lists all the registers in mapping tables, in address order.

5.1 Register details

Register	Address	Description
GPIO_PRT0_DR	0x40040000	Port output data register
GPIO_PRT0_PS	0x40040004	Port IO pad state register
GPIO_PRT0_PC	0x40040008	Port configuration register
GPIO_PRT0_INTR_CFG	0x4004000C	Port interrupt configuration register
GPIO_PRT0_INTR	0x40040010	Port interrupt status register
GPIO_PRT0_PC2	0x40040018	Port configuration register 2
GPIO_PRT0_MSC_ANA	0x40040024	Port MSCv3 AMUX enable
GPIO_PRT0_DR_SET	0x40040040	Port output data set register
GPIO_PRT0_DR_CLR	0x40040044	Port output data clear register
GPIO_PRT0_DR_INV	0x40040048	Port output data invert register
GPIO_PRT1_DR	0x40040100	Port output data register
GPIO_PRT1_PS	0x40040104	Port IO pad state register
GPIO_PRT1_PC	0x40040108	Port configuration register
GPIO_PRT1_INTR_CFG	0x4004010C	Port interrupt configuration register
GPIO_PRT1_INTR	0x40040110	Port interrupt status register
GPIO_PRT1_PC2	0x40040118	Port configuration register 2
GPIO_PRT1_MSC_ANA	0x40040124	Port MSCv3 AMUX enable
GPIO_PRT1_DR_SET	0x40040140	Port output data set register. See GPIO_PRT0_DR_SET for the details of bit fields.
GPIO_PRT1_DR_CLR	0x40040144	Port output data clear register. See GPIO_PRT0_DR_CLR for the details of bit fields.
GPIO_PRT1_DR_INV	0x40040148	Port output data invert register. See GPIO_PRT0_DR_INV for the details of bit fields.
GPIO_PRT2_DR	0x40040200	Port output data register. See GPIO_PRT0_DR for the details of bit fields.
GPIO_PRT2_PS	0x40040204	Port IO pad state register. See GPIO_PRT0_PS for the details of bit fields.
GPIO_PRT2_PC	0x40040208	Port configuration register. See GPIO_PRT0_PC for the details of bit fields.
GPIO_PRT2_INTR_CFG	0x4004020C	Port interrupt configuration register. See GPIO_PRT0_INTR_CFG for the details of bit fields.

General Purpose IO (GPIO) registers

Register	Address	Description
GPIO_PRT2_INTR	0x40040210	Port interrupt status register. See GPIO_PRT0_INTR for the details of bit fields.
GPIO_PRT2_PC2	0x40040218	Port configuration register 2. See GPIO_PRT0_PC2 for the details of bit fields.
GPIO_PRT2_MSC_ANA	0x40040224	Port MSCv3 AMUX enable. See GPIO_PRT0_MSC_ANA for the details of bit fields.
GPIO_PRT2_DR_SET	0x40040240	Port output data set register. See GPIO_PRT0_DR_SET for the details of bit fields.
GPIO_PRT2_DR_CLR	0x40040244	Port output data clear register. See GPIO_PRT0_DR_CLR for the details of bit fields.
GPIO_PRT2_DR_INV	0x40040248	Port output data invert register. See GPIO_PRT0_DR_INV for the details of bit fields.
GPIO_PRT3_DR	0x40040300	Port output data register
GPIO_PRT3_PS	0x40040304	Port IO pad state register
GPIO_PRT3_PC	0x40040308	Port configuration register
GPIO_PRT3_INTR_CFG	0x4004030C	Port interrupt configuration register
GPIO_PRT3_INTR	0x40040310	Port interrupt status register
GPIO_PRT3_PC2	0x40040318	Port configuration register 2
GPIO_PRT3_MSC_ANA	0x40040324	Port MSCv3 AMUX enable
GPIO_PRT3_DR_SET	0x40040340	Port output data set register. See GPIO_PRT0_DR_SET for the details of bit fields.
GPIO_PRT3_DR_CLR	0x40040344	Port output data clear register. See GPIO_PRT0_DR_CLR for the details of bit fields.
GPIO_PRT3_DR_INV	0x40040348	Port output data invert register. See GPIO_PRT0_DR_INV for the details of bit fields.
GPIO_PRT4_DR	0x40040400	Port output data register. See GPIO_PRT3_DR for the details of bit fields.
GPIO_PRT4_PS	0x40040404	Port IO pad state register. See GPIO_PRT3_PS for the details of bit fields.
GPIO_PRT4_PC	0x40040408	Port configuration register. See GPIO_PRT3_PC for the details of bit fields.
GPIO_PRT4_INTR_CFG	0x4004040C	Port interrupt configuration register. See GPIO_PRT3_INTR_CFG for the details of bit fields.
GPIO_PRT4_INTR	0x40040410	Port interrupt status register. See GPIO_PRT3_INTR for the details of bit fields.
GPIO_PRT4_PC2	0x40040418	Port configuration register 2. See GPIO_PRT3_PC2 for the details of bit fields.

General Purpose IO (GPIO) registers

Register	Address	Description
GPIO_PRT4_MSC_ANA	0x40040424	Port MSCv3 AMUX enable. See GPIO_PRT3_MSC_ANA for the details of bit fields.
GPIO_PRT4_DR_SET	0x40040440	Port output data set register. See GPIO_PRT0_DR_SET for the details of bit fields.
GPIO_PRT4_DR_CLR	0x40040444	Port output data clear register. See GPIO_PRT0_DR_CLR for the details of bit fields.
GPIO_PRT4_DR_INV	0x40040448	Port output data invert register. See GPIO_PRT0_DR_INV for the details of bit fields.
GPIO_INTR_CAUSE	0x40041000	Interrupt port cause register
GPIO_DFT_IO_TEST	0x40041010	IO SELF TEST control register for DfT purposes only

5.1.1 GPIO_PRT0_DR

Port output data register

Address: 0x40040000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	RW	RW	RW	RW
HW Access	None		RW	RW	RW	RW	RW	RW
Name	None [7:6]		DATA5	DATA4	DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
5	DATA5	IO pad 5 output data. Default Value: 0
4	DATA4	IO pad 4 output data. Default Value: 0
3	DATA3	IO pad 3 output data. Default Value: 0
2	DATA2	IO pad 2 output data. Default Value: 0
1	DATA1	IO pad 1 output data. Default Value: 0
0	DATA0	IO pad 0 output data. Default Value: 0

5.1.2 GPIO_PRT0_PS

Port IO pad state register

Address: 0x40040004

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		R	R	R	R	R	R
HW Access	None		W	W	W	W	W	W
Name	None [7:6]		DATA5	DATA4	DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	FLT_DATA	Reads of this register return the logical state of the filtered pin. Default Value: 0
5	DATA5	IO pad 5 state. Default Value: 0
4	DATA4	IO pad 4 state. Default Value: 0
3	DATA3	IO pad 3 state. Default Value: 0
2	DATA2	IO pad 2 state. Default Value: 0
1	DATA1	IO pad 1 state. Default Value: 0
0	DATA0	IO pad 0 state: 1: Logic high, if the pin voltage is above the input buffer threshold, logic high. 0: Logic low, if the pin voltage is below that threshold, logic low. If the drive mode for the pin is set to high Z Analog, the pin state will read 0 independent of the voltage on the pin. Default Value: 0

5.1.3 GPIO_PRT0_PC

Port configuration register

Address: 0x40040008

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW			RW		
HW Access	R		R			R		
Name	DM2 [7:6]		DM1 [5:3]			DM0 [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	RW	RW			RW			RW
HW Access	R	R			R			R
Name	DM5	DM4 [14:12]			DM3 [11:9]			DM2

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW	
HW Access	None						R	
Name	None [23:18]						DM5 [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	RW		None				RW	RW
HW Access	R		None				R	R
Name	PORT_IB_MODE_SEL [31:30]		None [29:26]				PORT_SLOW	PORT_VTRIP_SEL

Bits	Name	Description
31 : 30	PORT_IB_MODE_SEL	This field selects the input buffer reference. The size (1 or 2 bits) and functionality is dependent on the IO cell. For GPIOv2 IO cells, bit PORT_IB_MODE_SEL[1] is not used (GPIOv2 IO cell replaces GPIO IO cell): "0"/"2": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1"/"3": vcchib. For GPIO_OVTv2 and SIOv2 IO cells: "0": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1": vcchib. "2": OVT. "3": Reference (possibly from reference generator cell). For SIO IO cell, this field is present but not used as the SIO IO cell does not provide input buffer mode select functionality (SIOv2 IO cell will replace SIO IO cell, as soon as it is available). For GPIOV1P2 and GPIOV1P2_I2C cells, PC.PORT_IB_MODE_SEL unused. Refer to DS register. Default Value: 0
25	PORT_SLOW	This field controls the output edge rate of all pins on the port: '0': fast. '1': slow. Default Value: 0

5.1.3 GPIO_PRT0_PC (continued)

24	PORT_VTRIP_SEL	The GPIO cells include a VTRIP_SEL signal to alter the input buffer voltage. Note: this bit is ignored for SIO ports, the VTRIP_SEL settings in the SIO register are used instead (a separate VTRIP_SEL is provided for each pin pair). 0: input buffer functions as a CMOS input buffer. 1: input buffer functions as a LVTTTL input buffer. For GPIOV1P2 and GPIOV1P_I2C cells, PC.PORT_VTRIP_SEL is unused. Refer to DS register Default Value: 0
17 : 15	DM5	The GPIO drive mode for IO pad 5. Default Value: 0
14 : 12	DM4	The GPIO drive mode for IO pad 4. Default Value: 0
11 : 9	DM3	The GPIO drive mode for IO pad 3. Default Value: 0
8 : 6	DM2	The GPIO drive mode for IO pad 2. Default Value: 0
5 : 3	DM1	The GPIO drive mode for IO pad 1. Default Value: 0
2 : 0	DM0	The GPIO drive mode for IO pad 0. Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the HSIOM is properly configured (HSIOM_PRT_SELx) before turning the IO on here to avoid producing glitches on the bus. Default Value: 0 0x0: OFF : Mode 0 (analog mode): Output buffer off (high Z). Input buffer off. 0x1: INPUT : Mode 1: Output buffer off (high Z). Input buffer on. 0x2: 0_PU : Mode 2: Strong pull down ('0'), weak/resistive pull up (PU). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x3: PD_1 : Mode 3: Weak/resistive pull down (PD), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C: Weak pull down only. 0x4: 0_Z : Mode 4: Strong pull down ('0'), open drain (pull up off). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x5: Z_1 : Mode 5: Open drain (pull down off), strong pull up ('1'). Input buffer on. Illegal for GPIOV1P2_I2C 0x6: 0_1 : Mode 6: Strong pull down ('0'), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C, Strong pull down only.

5.1.3 GPIO_PRT0_PC (continued)

0x7: PD_PU :

Mode 7: Weak/resistive pull down (PD), weak/resistive pull up (PU). Input buffer on.
For GPIOV1P2_I2C: Weak pull down only.

5.1.4 GPIO_PRT0_INTR_CFG

Port interrupt configuration register

Address: 0x4004000C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW		RW		RW	
HW Access	R		R		R		R	
Name	EDGE3_SEL [7:6]		EDGE2_SEL [5:4]		EDGE1_SEL [3:2]		EDGE0_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW		RW	
HW Access	None				R		R	
Name	None [15:12]				EDGE5_SEL [11:10]		EDGE4_SEL [9:8]	

Bits	23	22	21	20	19	18	17	16
SW Access	None				RW		RW	
HW Access	None				R		R	
Name	None [23:21]				FLT_SEL [20:18]		FLT_EDGE_SEL [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
20 : 18	FLT_SEL	Selects which pin is routed through the 50ns glitch filter to provide a glitch-safe interrupt. Default Value: 0
17 : 16	FLT_EDGE_SEL	Same for the glitch filtered pin (selected by FLT_SEL). Default Value: 0 0x0: DISABLE : Disabled 0x1: RISING : Rising edge 0x2: FALLING : Falling edge 0x3: BOTH : Both rising and falling edges
11 : 10	EDGE5_SEL	Sets which edge will trigger an IRQ for IO pad 5. Default Value: 0
9 : 8	EDGE4_SEL	Sets which edge will trigger an IRQ for IO pad 4. Default Value: 0

5.1.4 GPIO_PRT0_INTR_CFG (continued)

7 : 6	EDGE3_SEL	Sets which edge will trigger an IRQ for IO pad 3. Default Value: 0
5 : 4	EDGE2_SEL	Sets which edge will trigger an IRQ for IO pad 2. Default Value: 0
3 : 2	EDGE1_SEL	Sets which edge will trigger an IRQ for IO pad 1. Default Value: 0
1 : 0	EDGE0_SEL	Sets which edge will trigger an IRQ for IO pad 0. Default Value: 0

0x0: DISABLE :

Disabled

0x1: RISING :

Rising edge

0x2: FALLING :

Falling edge

0x3: BOTH :

Both rising and falling edges

5.1.5 GPIO_PRT0_INTR

Port interrupt status register

Address: 0x40040010

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW1C	RW1C	RW1C	RW1C	RW1C	RW1C
HW Access	None		A	A	A	A	A	A
Name	None [7:6]		DATA5	DATA4	DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1C
HW Access	None							A
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None		R	R	R	R	R	R
HW Access	None		W	W	W	W	W	W
Name	None [23:22]		PS_DATA5	PS_DATA4	PS_DATA3	PS_DATA2	PS_DATA1	PS_DATA0

Bits	31	30	29	28	27	26	25	24
SW Access	None							R
HW Access	None							W
Name	None [31:25]							PS_FLT_DATA

Bits	Name	Description
24	PS_FLT_DATA	This is a duplicate of the contents of the PS register, provided here to allow reading of both pin state and interrupt state of the port in a single read operation. Default Value: 0
21	PS_DATA5	Default Value: 0
20	PS_DATA4	Default Value: 0
19	PS_DATA3	Default Value: 0
18	PS_DATA2	Default Value: 0
17	PS_DATA1	Default Value: 0
16	PS_DATA0	` Default Value: 0
8	FLT_DATA	Deglitched interrupt pending (selected by FLT_SEL). Default Value: 0
5	DATA5	Interrupt pending on IO pad 5. Firmware writes 1 to clear the interrupt. Default Value: 0
4	DATA4	Interrupt pending on IO pad 4. Firmware writes 1 to clear the interrupt. Default Value: 0
3	DATA3	Interrupt pending on IO pad 3. Firmware writes 1 to clear the interrupt. Default Value: 0
2	DATA2	Interrupt pending on IO pad 2. Firmware writes 1 to clear the interrupt. Default Value: 0

5.1.5 GPIO_PRT0_INTR (continued)

1	DATA1	Interrupt pending on IO pad 1. Firmware writes 1 to clear the interrupt. Default Value: 0
0	DATA0	Interrupt pending on IO pad 0. Firmware writes 1 to clear the interrupt. Default Value: 0

5.1.6 GPIO_PRT0_PC2

Port configuration register 2

Address: 0x40040018

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	RW	RW	RW	RW
HW Access	None		R	R	R	R	R	R
Name	None [7:6]		INP_DIS5	INP_DIS4	INP_DIS3	INP_DIS2	INP_DIS1	INP_DIS0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
5	INP_DIS5	Disables the input buffer for IO pad 5. Default Value: 0
4	INP_DIS4	Disables the input buffer for IO pad 4. Default Value: 0
3	INP_DIS3	Disables the input buffer for IO pad 3. Default Value: 0
2	INP_DIS2	Disables the input buffer for IO pad 2. Default Value: 0
1	INP_DIS1	Disables the input buffer for IO pad 1. Default Value: 0
0	INP_DIS0	Disables the input buffer for IO pad 0 independent of the port control drive mode (PC.DM). This bit should be set when analog signals are present on the pin and PC.DM != 0 is required to use the output driver. Default Value: 0

5.1.7 GPIO_PRT0_MSC_ANA

Port MSCv3 AMUX enable

Address: 0x40040024

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	RW	RW	RW	RW
HW Access	None		R	R	R	R	R	R
Name	None [7:6]		DATA5	DATA4	DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
5	DATA5	IO pad 5 MSC_ANA_EN Default Value: 0
4	DATA4	IO pad 4 MSC_ANA_EN Default Value: 0
3	DATA3	IO pad 3 MSC_ANA_EN Default Value: 0
2	DATA2	IO pad 2 MSC_ANA_EN Default Value: 0
1	DATA1	IO pad 1 MSC_ANA_EN. Default Value: 0
0	DATA0	IO pad 0 MSC_ANA_EN Default Value: 0

5.1.8 GPIO_PRT0_DR_SET

Port output data set register

Address: 0x40040040

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	A							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	DATA	IO pad i: '0': Output state DR.DATA[i] not affected. '1': Output state DR.DATA[i] set to '1'. Default Value: 0

5.1.9 GPIO_PRT0_DR_CLR

Port output data clear register

Address: 0x40040044

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	A							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	DATA	IO pad i: '0': Output state DR.DATA[i] not affected. '1': Output state DR.DATA[i] set to '0'. Default Value: 0

5.1.10 GPIO_PRT0_DR_INV

Port output data invert register

Address: 0x40040048

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	A							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	DATA	IO pad i: '0': Output state DR.DATA[i] not affected. '1': Output state DR.DATA[i] inverted ('0' => '1', '1' => '0'). Default Value: 0

5.1.11 GPIO_PRT1_DR

Port output data register

Address: 0x40040100

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							RW
Name	None [7:1]							DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	DATA0	IO pad 0 output data. Default Value: 0

5.1.12 GPIO_PRT1_PS

Port IO pad state register

Address: 0x40040104

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							R
HW Access	None							W
Name	None [7:1]							DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	FLT_DATA	Reads of this register return the logical state of the filtered pin. Default Value: 0
0	DATA0	IO pad 0 state: 1: Logic high, if the pin voltage is above the input buffer threshold, logic high. 0: Logic low, if the pin voltage is below that threshold, logic low. If the drive mode for the pin is set to high Z Analog, the pin state will read 0 independent of the voltage on the pin. Default Value: 0

5.1.13 GPIO_PRT1_PC

Port configuration register

Address: 0x40040108

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW		
HW Access	None					R		
Name	None [7:3]					DM0 [2:0]		
Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
SW Access	RW		None				RW	RW
HW Access	R		None				R	R
Name	PORT_IB_MODE_SEL [31:30]		None [29:26]				PORT_SLOW	PORT_VTRIP_SEL

Bits	Name	Description
31 : 30	PORT_IB_MODE_SEL	This field selects the input buffer reference. The size (1 or 2 bits) and functionality is dependent on the IO cell. For GPIOv2 IO cells, bit PORT_IB_MODE_SEL[1] is not used (GPIOv2 IO cell replaces GPIO IO cell): "0"/"2": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1"/"3": vcchib. For GPIO_OVTv2 and SIOv2 IO cells: "0": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1": vcchib. "2": OVT. "3": Reference (possibly from reference generator cell). For SIO IO cell, this field is present but not used as the SIO IO cell does not provide input buffer mode select functionality (SIOv2 IO cell will replace SIO IO cell, as soon as it is available). For GPIOV1P2 and GPIOV1P2_I2C cells, PC.PORT_IB_MODE_SEL unused. Refer to DS register. Default Value: 0
25	PORT_SLOW	This field controls the output edge rate of all pins on the port: '0': fast. '1': slow. Default Value: 0

5.1.13 GPIO_PRT1_PC (continued)

24	PORT_VTRIP_SEL	The GPIO cells include a VTRIP_SEL signal to alter the input buffer voltage. Note: this bit is ignored for SIO ports, the VTRIP_SEL settings in the SIO register are used instead (a separate VTRIP_SEL is provided for each pin pair). 0: input buffer functions as a CMOS input buffer. 1: input buffer functions as a LVTTTL input buffer. For GPIOV1P2 and GPIOV1P_I2C cells, PC.PORT_VTRIP_SEL is unused. Refer to DS register Default Value: 0
2 : 0	DM0	The GPIO drive mode for IO pad 0. Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the HSIOM is properly configured (HSIOM_PRT_SELx) before turning the IO on here to avoid producing glitches on the bus. Default Value: 0 0x0: OFF : Mode 0 (analog mode): Output buffer off (high Z). Input buffer off. 0x1: INPUT : Mode 1: Output buffer off (high Z). Input buffer on. 0x2: 0_PU : Mode 2: Strong pull down ('0'), weak/resistive pull up (PU). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x3: PD_1 : Mode 3: Weak/resistive pull down (PD), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C: Weak pull down only. 0x4: 0_Z : Mode 4: Strong pull down ('0'), open drain (pull up off). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x5: Z_1 : Mode 5: Open drain (pull down off), strong pull up ('1'). Input buffer on. Illegal for GPIOV1P2_I2C 0x6: 0_1 : Mode 6: Strong pull down ('0'), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x7: PD_PU : Mode 7: Weak/resistive pull down (PD), weak/resistive pull up (PU). Input buffer on. For GPIOV1P2_I2C: Weak pull down only.

5.1.14 GPIO_PRT1_INTR_CFG

Port interrupt configuration register

Address: 0x4004010C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW	
HW Access	None						R	
Name	None [7:2]						EDGE0_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None				RW			RW
HW Access	None				R			R
Name	None [23:21]				FLT_SEL [20:18]			FLT_EDGE_SEL [17:16]

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
20 : 18	FLT_SEL	Selects which pin is routed through the 50ns glitch filter to provide a glitch-safe interrupt. Default Value: 0
17 : 16	FLT_EDGE_SEL	Same for the glitch filtered pin (selected by FLT_SEL). Default Value: 0 0x0: DISABLE : Disabled 0x1: RISING : Rising edge 0x2: FALLING : Falling edge 0x3: BOTH : Both rising and falling edges
1 : 0	EDGE0_SEL	Sets which edge will trigger an IRQ for IO pad 0. Default Value: 0

5.1.14 GPIO_PRT1_INTR_CFG (continued)

0x0: DISABLE :

Disabled

0x1: RISING :

Rising edge

0x2: FALLING :

Falling edge

0x3: BOTH :

Both rising and falling edges

5.1.15 GPIO_PRT1_INTR

Port interrupt status register

Address: 0x40040110

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW1C
HW Access	None							A
Name	None [7:1]							DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1C
HW Access	None							A
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None							R
HW Access	None							W
Name	None [23:17]							PS_DATA0

Bits	31	30	29	28	27	26	25	24
SW Access	None							R
HW Access	None							W
Name	None [31:25]							PS_FLT_- DATA

Bits	Name	Description
24	PS_FLT_DATA	This is a duplicate of the contents of the PS register, provided here to allow reading of both pin state and interrupt state of the port in a single read operation. Default Value: 0
16	PS_DATA0	` Default Value: 0
8	FLT_DATA	Deglitched interrupt pending (selected by FLT_SEL). Default Value: 0
0	DATA0	Interrupt pending on IO pad 0. Firmware writes 1 to clear the interrupt. Default Value: 0

5.1.16 GPIO_PRT1_PC2

Port configuration register 2

Address: 0x40040118

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							R
Name	None [7:1]							INP_DIS0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	INP_DIS0	Disables the input buffer for IO pad 0 independent of the port control drive mode (PC.DM). This bit should be set when analog signals are present on the pin and PC.DM != 0 is required to use the output driver. Default Value: 0

5.1.17 GPIO_PRT1_MSC_ANA

Port MSCv3 AMUX enable

Address: 0x40040124

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							R
Name	None [7:1]							DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	DATA0	IO pad 0 MSC_ANA_EN Default Value: 0

5.1.18 GPIO_PRT3_DR

Port output data register

Address: 0x40040300

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				RW	RW	RW	RW
Name	None [7:4]				DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	DATA3	IO pad 3 output data. Default Value: 0
2	DATA2	IO pad 2 output data. Default Value: 0
1	DATA1	IO pad 1 output data. Default Value: 0
0	DATA0	IO pad 0 output data. Default Value: 0

5.1.19 GPIO_PRT3_PS

Port IO pad state register

Address: 0x40040304

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [7:4]				DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	FLT_DATA	Reads of this register return the logical state of the filtered pin. Default Value: 0
3	DATA3	IO pad 3 state. Default Value: 0
2	DATA2	IO pad 2 state. Default Value: 0
1	DATA1	IO pad 1 state. Default Value: 0
0	DATA0	IO pad 0 state: 1: Logic high, if the pin voltage is above the input buffer threshold, logic high. 0: Logic low, if the pin voltage is below that threshold, logic low. If the drive mode for the pin is set to high Z Analog, the pin state will read 0 independent of the voltage on the pin. Default Value: 0

5.1.20 GPIO_PRT3_PC

Port configuration register

Address: 0x40040308

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW			RW		
HW Access	R		R			R		
Name	DM2 [7:6]		DM1 [5:3]			DM0 [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW			RW
HW Access	None				R			R
Name	None [15:12]				DM3 [11:9]			DM2

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW		None				RW	RW
HW Access	R		None				R	R
Name	PORT_IB_MODE_SEL [31:30]		None [29:26]				PORT_SLOW	PORT_VTRIP_SEL

Bits	Name	Description
31 : 30	PORT_IB_MODE_SEL	This field selects the input buffer reference. The size (1 or 2 bits) and functionality is dependent on the IO cell. For GPIOv2 IO cells, bit PORT_IB_MODE_SEL[1] is not used (GPIOv2 IO cell replaces GPIO IO cell): "0"/"2": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1"/"3": vcchib. For GPIO_OVTv2 and SIOv2 IO cells: "0": CMOS input buffer (PORT_VTRIP_SEL is '0'), LVTTTL input buffer (PORT_VTRIP_SEL is '1') "1": vcchib. "2": OVT. "3": Reference (possibly from reference generator cell). For SIO IO cell, this field is present but not used as the SIO IO cell does not provide input buffer mode select functionality (SIOv2 IO cell will replace SIO IO cell, as soon as it is available). For GPIOV1P2 and GPIOV1P2_I2C cells, PC.PORT_IB_MODE_SEL unused. Refer to DS register. Default Value: 0
25	PORT_SLOW	This field controls the output edge rate of all pins on the port: '0': fast. '1': slow. Default Value: 0

5.1.20 GPIO_PRT3_PC (continued)

24	PORT_VTRIP_SEL	The GPIO cells include a VTRIP_SEL signal to alter the input buffer voltage. Note: this bit is ignored for SIO ports, the VTRIP_SEL settings in the SIO register are used instead (a separate VTRIP_SEL is provided for each pin pair). 0: input buffer functions as a CMOS input buffer. 1: input buffer functions as a LVTTTL input buffer. For GPIOV1P2 and GPIOV1P_I2C cells, PC.PORT_VTRIP_SEL is unused. Refer to DS register Default Value: 0
11 : 9	DM3	The GPIO drive mode for IO pad 3. Default Value: 0
8 : 6	DM2	The GPIO drive mode for IO pad 2. Default Value: 0
5 : 3	DM1	The GPIO drive mode for IO pad 1. Default Value: 0
2 : 0	DM0	The GPIO drive mode for IO pad 0. Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the HSIOM is properly configured (HSIOM_PRT_SELx) before turning the IO on here to avoid producing glitches on the bus. Default Value: 0 0x0: OFF : Mode 0 (analog mode): Output buffer off (high Z). Input buffer off. 0x1: INPUT : Mode 1: Output buffer off (high Z). Input buffer on. 0x2: 0_PU : Mode 2: Strong pull down ('0'), weak/resistive pull up (PU). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x3: PD_1 : Mode 3: Weak/resistive pull down (PD), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C: Weak pull down only. 0x4: 0_Z : Mode 4: Strong pull down ('0'), open drain (pull up off). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x5: Z_1 : Mode 5: Open drain (pull down off), strong pull up ('1'). Input buffer on. Illegal for GPIOV1P2_I2C 0x6: 0_1 : Mode 6: Strong pull down ('0'), strong pull up ('1'). Input buffer on. For GPIOV1P2_I2C, Strong pull down only. 0x7: PD_PU : Mode 7: Weak/resistive pull down (PD), weak/resistive pull up (PU). Input buffer on. For GPIOV1P2_I2C: Weak pull down only.

5.1.21 GPIO_PRT3_INTR_CFG

Port interrupt configuration register

Address: 0x4004030C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW		RW		RW	
HW Access	R		R		R		R	
Name	EDGE3_SEL [7:6]		EDGE2_SEL [5:4]		EDGE1_SEL [3:2]		EDGE0_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None			RW			RW	
HW Access	None			R			R	
Name	None [23:21]			FLT_SEL [20:18]			FLT_EDGE_SEL [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
20 : 18	FLT_SEL	Selects which pin is routed through the 50ns glitch filter to provide a glitch-safe interrupt. Default Value: 0
17 : 16	FLT_EDGE_SEL	Same for the glitch filtered pin (selected by FLT_SEL). Default Value: 0 0x0: DISABLE : Disabled 0x1: RISING : Rising edge 0x2: FALLING : Falling edge 0x3: BOTH : Both rising and falling edges
7 : 6	EDGE3_SEL	Sets which edge will trigger an IRQ for IO pad 3. Default Value: 0
5 : 4	EDGE2_SEL	Sets which edge will trigger an IRQ for IO pad 2. Default Value: 0

5.1.21 GPIO_PRT3_INTR_CFG (continued)

3 : 2	EDGE1_SEL	Sets which edge will trigger an IRQ for IO pad 1. Default Value: 0
-------	-----------	---

1 : 0	EDGE0_SEL	Sets which edge will trigger an IRQ for IO pad 0. Default Value: 0
-------	-----------	---

0x0: DISABLE :

Disabled

0x1: RISING :

Rising edge

0x2: FALLING :

Falling edge

0x3: BOTH :

Both rising and falling edges

5.1.22 GPIO_PRT3_INTR

Port interrupt status register

Address: 0x40040310

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW1C	RW1C	RW1C	RW1C
HW Access	None				A	A	A	A
Name	None [7:4]				DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1C
HW Access	None							A
Name	None [15:9]							FLT_DATA

Bits	23	22	21	20	19	18	17	16
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [23:20]				PS_DATA3	PS_DATA2	PS_DATA1	PS_DATA0

Bits	31	30	29	28	27	26	25	24
SW Access	None							R
HW Access	None							W
Name	None [31:25]							PS_FLT_DATA

Bits	Name	Description
24	PS_FLT_DATA	This is a duplicate of the contents of the PS register, provided here to allow reading of both pin state and interrupt state of the port in a single read operation. Default Value: 0
19	PS_DATA3	Default Value: 0
18	PS_DATA2	Default Value: 0
17	PS_DATA1	Default Value: 0
16	PS_DATA0	Default Value: 0
8	FLT_DATA	Deglitched interrupt pending (selected by FLT_SEL). Default Value: 0
3	DATA3	Interrupt pending on IO pad 3. Firmware writes 1 to clear the interrupt. Default Value: 0
2	DATA2	Interrupt pending on IO pad 2. Firmware writes 1 to clear the interrupt. Default Value: 0
1	DATA1	Interrupt pending on IO pad 1. Firmware writes 1 to clear the interrupt. Default Value: 0
0	DATA0	Interrupt pending on IO pad 0. Firmware writes 1 to clear the interrupt. Default Value: 0

5.1.23 GPIO_PRT3_PC2

Port configuration register 2

Address: 0x40040318

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [7:4]				INP_DIS3	INP_DIS2	INP_DIS1	INP_DIS0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	INP_DIS3	Disables the input buffer for IO pad 3. Default Value: 0
2	INP_DIS2	Disables the input buffer for IO pad 2. Default Value: 0
1	INP_DIS1	Disables the input buffer for IO pad 1. Default Value: 0
0	INP_DIS0	Disables the input buffer for IO pad 0 independent of the port control drive mode (PC.DM). This bit should be set when analog signals are present on the pin and PC.DM != 0 is required to use the output driver. Default Value: 0

5.1.24 GPIO_PRT3_MSC_ANA

Port MSCv3 AMUX enable

Address: 0x40040324

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [7:4]				DATA3	DATA2	DATA1	DATA0

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	DATA3	IO pad 3 MSC_ANA_EN Default Value: 0
2	DATA2	IO pad 2 MSC_ANA_EN Default Value: 0
1	DATA1	IO pad 1 MSC_ANA_EN. Default Value: 0
0	DATA0	IO pad 0 MSC_ANA_EN Default Value: 0

5.1.25 GPIO_INTR_CAUSE

Interrupt port cause register

Address: 0x40041000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R				
HW Access	None			W				
Name	None [7:5]			PORT_INT [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
4 : 0	PORT_INT	Each IO port has an associated bit field in this register. The bit field reflects the IO port's interrupt line (bit field i reflects "interrupts_gpio[i]" for IO port i). The register is used when the system uses a shared/combined interrupt line "interrupt_gpio". The SW ISR reads the register to determine which IO port(s) is responsible for the shared/combined interrupt line "interrupt_gpio". Once, the IO port(s) is determined, the IO port's INTR register is read to determine the IO pad(s) in the IO port that caused the interrupt. Default Value: 0

5.1.26 GPIO_DFT_IO_TEST

IO SELF TEST control register for DfT purposes only

Address: 0x40041010

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW	
HW Access	None						R	
Name	None [7:2]						DFT_IO_TEST_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None			RW	RW	RW	RW	RW
HW Access	None			R	R	R	R	R
Name	None [15:13]			DFT_ANA_POL_0	DFT_ANA_SEL_0	DFT_ANALOG_EN_0	DFT_OE_N_0	DFT_HLD_OVR_0

Bits	23	22	21	20	19	18	17	16
SW Access	None			RW	RW	RW	RW	RW
HW Access	None			R	R	R	R	R
Name	None [23:21]			DFT_ANA_POL_1	DFT_ANA_SEL_1	DFT_ANALOG_EN_1	DFT_OE_N_1	DFT_HLD_OVR_1

Bits	31	30	29	28	27	26	25	24
SW Access	None			RW	RW	RW	RW	RW
HW Access	None			R	R	R	R	R
Name	None [31:29]			DFT_ANA_POL_2	DFT_ANA_SEL_2	DFT_ANALOG_EN_2	DFT_OE_N_2	DFT_HLD_OVR_2

Bits	Name	Description
28	DFT_ANA_POL_2	"analog_pol" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_pol" of all IO cells other than ADFT-0/1. TEST_ANA: Connects to "analog_pol" of all IO cells other than IO_TEST_0/1. TEST_GEN: Connects to "analog_pol" of all IO cells. Default Value: 0
27	DFT_ANA_SEL_2	"analog_sel" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_sel" of all IO cells other than ADFT-0/1. TEST_ANA: Connects to "analog_sel" of all IO cells other than IO_TEST_0/1. TEST_GEN: Connects to "analog_sel" of all IO cells. Default Value: 0
26	DFT_ANALOG_EN_2	"analog_en" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_en" of all IO cells other than ADFT-0/1. TEST_ANA: DFT_ANALOG_EN_2 && DM[0] connects to "analog_en" of all IO cells other than IO_TEST_0/1. TEST_GEN: Connects to "analog_en" of all IO cells Default Value: 0
25	DFT_OE_N_2	"oe_n" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "oe_n" of all IO cells other than ADFT-0/1. TEST_ANA: Connects to "oe_n" of all IO cells other than IO_TEST_0/1. TEST_GEN: Connects to "oe_n" of all IO cells Default Value: 1

5.1.26 GPIO_DFT_IO_TEST (continued)

24	DFT_HLD_OVR_2	"hld_ovr" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "hld_ovr" of all IO cells other than ADFT-0/1 . TEST_ANA: Connects to "hld_ovr" of all IO cells other than IO_TEST_0/1. TEST_GEN: Connects to "hld_ovr" of all IO cells. Default Value: 0
20	DFT_ANA_POL_1	"analog_pol" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_pol" of the ADFT-1 assigned IO cell. TEST_ANA: Connects to "analog_pol" of the IO_TEST_1 assigned IO cell. TEST_GEN: not used. Default Value: 0
19	DFT_ANA_SEL_1	"analog_sel" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_sel" of the ADFT-1 assigned IO cell. TEST_ANA: Connects to "analog_sel" of the IO_TEST_1 assigned IO cell. TEST_GEN: not used. Default Value: 0
18	DFT_ANALOG_EN_1	"analog_en" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_en" of the ADFT-1 assigned IO cell. TEST_ANA: Connects to "analog_en" of the IO_TEST_1 assigned IO cell. TEST_GEN: not used. Default Value: 0
17	DFT_OE_N_1	"oe_n" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "oe_n" of the ADFT-1 assigned IO cell. TEST_ANA: Connects to "oe_n" of the IO_TEST_1 assigned IO cell. TEST_GEN: not used. Default Value: 1
16	DFT_HLD_OVR_1	"hld_ovr" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "hld_ovr" of the ADFT-1 assigned IO cell. TEST_ANA: Connects to "hld_ovr" of the IO_TEST_1 assigned IO cell. TEST_GEN: not used. Default Value: 0
12	DFT_ANA_POL_0	"analog_pol" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_pol" of the ADFT-0 assigned IO cell. TEST_ANA: Connects to "analog_pol" of the IO_TEST_0 assigned IO cell. TEST_GEN: not used. Default Value: 0
11	DFT_ANA_SEL_0	"analog_sel" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_sel" of the ADFT-0 assigned IO cell. TEST_ANA: Connects to "analog_sel" of the IO_TEST_0 assigned IO cell. TEST_GEN: not used. Default Value: 0
10	DFT_ANALOG_EN_0	"analog_en" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "analog_en" of the ADFT-0 assigned IO cell. TEST_ANA: Connects to "analog_en" of the IO_TEST_0 assigned IO cell. TEST_GEN: not used. Default Value: 0
9	DFT_OE_N_0	"oe_n" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "oe_n" of the ADFT-0 assigned IO cell. TEST_ANA: Connects to "oe_n" of the IO_TEST_0 assigned IO cell. TEST_GEN: not used. Default Value: 1
8	DFT_HLD_OVR_0	"hld_ovr" DfT control for IO cells depending on DFT_IO_TEST_MODE as given below. TEST_ADFT: Connects to "hld_ovr" of the ADFT-0 assigned IO cell. TEST_ANA: Connects to "hld_ovr" of the IO_TEST_0 assigned IO cell. TEST_GEN: not used. Default Value: 0
1 : 0	DFT_IO_TEST_MODE	DfT IO SELF TEST mode: Default Value: 0

5.1.26 GPIO_DFT_IO_TEST (continued)

0x0: OFF :

Functional mode: disables the DFT IO SELF TEST; none of the "DFT_*" control signals from this register control the IO cells.

0x1: TEST_ADFT :

select this mode during ADFT testing to control "hld_ovr/oe_n/ analog_sel/ analog_pol/ analog_en" signals of IO cells as below:

the ADFT-0 assigned IO cell connects to: DFT_*_0;

the ADFT-1 assigned IO cell connects to: DFT_*_1;

All other IO cells connect to: DFT_*_2;

0x2: TEST_ANA :

select this mode for testing analog switches to control "hld_ovr/oe_n/analog_en/analog_sel/ analog_pol" signals of IO cells as below:

the IO_TEST_0 assigned IO cell connects to: DFT_*_0;

the IO_TEST_1 assigned IO cell connects to: DFT_*_1;

All other IO cells connect to: DFT_*_2;

0x3: TEST_GEN :

select this mode for generic testing to control "hld_ovr/oe_n/analog_en/analog_sel/analog_pol" signals of IO cells as below:

All IO cells connect to: DFT_*_2;

CPU Sub System (CPUSS) registers

6 CPU Sub System (CPUSS) registers

This section discusses the CPUSS registers. It lists all the registers in mapping tables, in address order.

6.1 Register details

Register	Address	Description
CPUSS_SYSREQ	0x40100004	SYSCALL control register
CPUSS_SYSARG	0x40100008	SYSARG control register
CPUSS_PROTECTION	0x4010000C	Protection control register
CPUSS_PRIV_ROM	0x40100010	ROM privilege register
CPUSS_PRIV_RAM	0x40100014	RAM privilege register
CPUSS_PRIV_FLASH	0x40100018	Flash privilege register
CPUSS_WOUNDING	0x4010001C	Wounding register
CPUSS_FLASH_CTL	0x40100030	FLASH control register
CPUSS_ROM_CTL	0x40100034	ROM control register

6.1.1 CPOSS_SYSREQ

SYSCALL control register

Address: 0x40100004

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	SYSCALL_COMMAND [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access								
Name	SYSCALL_COMMAND [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW	R	R	RW	RW	None		
HW Access	R	A	RW	A	R	None		
Name	SY- SCALL_RE Q	HMAS- TER_0	ROM_AC- CESS_EN	PRIVI- LEGED	DIS_RE- SET_VECT _REL	None [26:24]		

Bits	Name	Description
31	SYSCALL_REQ	CPU/DAP writes a '1' to this field to request a SystemCall. The HMASTER_0 field indicates the source of the write access. Setting this field to '1' immediate results in a NMI. The SystemCall NMI interrupt handler sets this field to '0' after servicing the request. Default Value: 0
30	HMASTER_0	Indicates the source of the write access to the SYSREQ register. '0': CPU write access. '1': DAP write access. For a SW write to the SYSREQ register, the HW will update this field based on the value of SY-SCALL_REQ. SYSCALL_REQ = 0 : the current source of write access is captured. SYSCALL_REQ = 1 : the previous value (captured when SYSCALL_REQ was 0), is retained/ maintained until the next SW write to this register. Default Value: 0
29	ROM_ACCESS_EN	Indicates that executing from Boot ROM is enabled. HW sets this field to '1', on reset or when the SystemCall NMI vector is fetched from Boot ROM. HW sets this field to '0', when the CPU is NOT executing from either Boot or System ROM. This bit is used for debug purposes only. Default Value: 1

6.1.1 CPOSS_SYSREQ (continued)

28	PRIVILEGED	Indicates whether the system is in privileged ('1') or user mode ('0'). Only CPU SW executing from ROM can set this field to '1' when ROM_ACCESS_EN is '1' (the CPU is executing a SystemCall NMI interrupt handler). Any other write to this field sets is to '0'. This field is used as the AHB-Lite hprot[1] signal to implement Cypress proprietary user/privileged modes. These modes are used to enable/disable access to specific MMIO registers and memory regions. Default Value: 1
27	DIS_RESET_VECT_REL	Disable Reset Vector fetch relocation: '0': CPU accesses to locations 0x0000:0000 - 0x0000:0007 are redirected to ROM. '1': CPU accesses to locations 0x0000:0000 - 0x0000:0007 are made to flash. Note that this field defaults to '0' on reset, ensuring actual reset vector fetches are always made to ROM. Note that this field does not affect DAP accesses. Flash DfT routines may set this bit to '1' to enable uninhibited read-back of programmed data in the first flash page. Default Value: 0
15 : 0	SYSCALL_COMMAND	Opcode of the system call being requested. Default Value: 0

6.1.2 CPUSS_SYSARG

SYSARG control register

Address: 0x40100008

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access								
Name	SYSCALL_ARG [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access								
Name	SYSCALL_ARG [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access								
Name	SYSCALL_ARG [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access								
Name	SYSCALL_ARG [31:24]							

Bits	Name	Description
31 : 0	SYSCALL_ARG	Argument to System Call specified in SYSREQ. Semantics of argument depends on system call made. Typically a pointer to a parameter block. Default Value: 0

6.1.3 CPUSS_PROTECTION

Protection control register

Address: 0x4010000C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				A			
Name	None [7:4]				PROTECTION_MODE [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW1S	RW	None					
HW Access	R	A	None					
Name	PROTECTION_LOCK	FLASH_LOCK	None [29:24]					

Bits	Name	Description
31	PROTECTION_LOCK	Setting this field will block (ignore) any further writes to the PROTECTION_MODE field in this register. Once '1', this field cannot be cleared. Default Value: 0
30	FLASH_LOCK	Setting this bit will force SPCIF.ADDRESS.AXA to be ignored, which prevents SM Flash from being erased or overwritten. It is used to indicate the DEAD protection mode. Writes to this field are ignored when PROTECTION_LOCK is '1' Default Value: 0
3 : 0	PROTECTION_MODE	Current protection mode; this field is available as a global signal everywhere in the system. Writes to this field are ignored when PROTECTION_LOCK is '1': 0b1xxx: BOOT 0b01xx: KILL 0b001x: PROTECTED 0b0001: OPEN 0b0000: VIRGIN (also used for DEAD mode, but then FLASH_LOCK is also set) Default Value: 15

6.1.4 CPOSS_PRIV_ROM

ROM privilege register

Address: 0x40100010

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	BROM_PROT_LIMIT [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	BROM_PROT_LIMIT	Indicates the limit where the privileged area of the Boot ROM partition starts in increments of 256 Bytes. "0": Entire Boot ROM is Privileged. "1": First 256 Bytes are User accessible. ... BROM_PROT_LIMIT >= "Boot ROM partition capacity": Entire Boot ROM partition is user mode accessible. Default Value: 0

6.1.5 CPUSS_PRIV_RAM

RAM privilege register

Address: 0x40100014

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	RAM_PROT_LIMIT [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							RAM_PROT_LIMIT

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8 : 0	RAM_PROT_LIMIT	Indicates the limit where the privileged area of SRAM starts in increments of 256 Bytes. "0": Entire SRAM is Privileged. "1": First 256 Bytes are User accessible. Any number larger than the size of the SRAM indicates that the entire SRAM is user mode accessible. Default Value: 0

6.1.6 CPOSS_PRIV_FLASH

Flash privilege register

Address: 0x40100018

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	FLASH_PROT_LIMIT [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW			
HW Access	None				R			
Name	None [15:12]				FLASH_PROT_LIMIT [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11 : 0	FLASH_PROT_LIMIT	Indicates the limit where the privileged area of flash starts in increments of 256 Bytes. "0": Entire flash is Privileged. "1": First 256 Bytes are User accessible. Any number larger than the size of the flash indicates that the entire flash is user mode accessible. Note that Supervisory rows are always User accessible. If FLASH_PROT_LIMIT defines a non-empty privileged area, the boot ROM will assume that a system call table exists at the beginning of the Flash privileged area and use it for all SystemCalls made using SYSREQ. Default Value: 0

6.1.7 CPUSS_WOUNDING

Wounding register

Address: 0x4010001C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None	RW1S			None	RW1S		
HW Access	None	R			None	R		
Name	None	FLASH_WOUND [22:20]			None	RAM_WOUND [18:16]		

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
22 : 20	FLASH_WOUND	Indicates the amount of accessible flash in this part. The value in this field is effectively write-once (it is only possible to set bits, not clear them). The remainder portion of flash is not accessible and will return an AHB-Lite bus error. "0": entire memory accessible "1": first 1/2 of the memory accessible "2": first 1/4 of the memory accessible "3": first 1/8 of the memory accessible "4": first 1/16 of the memory accessible "5": first 1/32 of the memory accessible "6": first 1/64 of the memory accessible "7": first 1/128 of the memory accessible (used for the DEAD protection mode) Default Value: 0
18 : 16	RAM_WOUND	Indicates the amount of accessible RAM 0 memory capacity in this part. The value in this field is effectively write-once (it is only possible to set bits, not clear them). The remainder portion of SRAM is not accessible and will return an AHB-Lite bus error. "0": entire memory accessible "1": first 1/2 of the memory accessible "2": first 1/4 of the memory accessible "3": first 1/8 of the memory accessible "4": first 1/16 of the memory accessible "5": first 1/32 of the memory accessible "6": first 1/64 of the memory accessible "7": first 1/128 of the memory accessible Default Value: 0

6.1.8 CPUSS_FLASH_CTL

FLASH control register

Address: 0x40100030

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	None		RW	
HW Access	None			R	None		R	
Name	None [7:5]			PREF_EN	None [3:2]		FLASH_WS [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							RW1C
Name	None [15:9]							FLASH_INVALIDATE

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	FLASH_INVALIDATE	1': Invalidates the content of the flash controller's buffers. Default Value: 0
4	PREF_EN	Prefetch enable: '0': disabled. This is a desirable setting when FLASH_WS is "0" or when predictable execution time is required. '1': enabled. Default Value: 0
1 : 0	FLASH_WS	Amount of ROM wait states: "0": 0 wait states (fast flash: [0, 24] MHz system frequency, slow flash: [0, 16] MHz system frequency) "1": 1 wait state (fast flash: [24, 48] MHz system frequency, slow flash: [16, 32] MHz system frequency) "2": 2 wait states (slow flash: [32, 48] MHz system frequency) "3": 3 wait states (can be used to give more time for flash access if 2 wait states are not sufficient) Default Value: 0

6.1.9 CPUSS_ROM_CTL

ROM control register

Address: 0x40100034

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							R
Name	None [7:1]							ROM_WS

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	ROM_WS	Amount of ROM wait states: '0': 0 wait states. Use this setting for newer, faster ROM design. Use this setting for older, slower ROM design and frequencies in the range [0, 24] MHz. '1': 1 wait state. Use this setting for older, slower ROM design and frequencies in the range <24, 48] MHz. Should always be set to 0. Default Value: 0

SPC Interface (SPCIF) registers

7 SPC Interface (SPCIF) registers

This section discusses the SPCIF registers. It lists all the registers in mapping tables, in address order.

7.1 Register details

Register	Address	Description
SPCIF_GEOMETRY	0x40110000	Flash/NVL geometry information
SPCIF_INTR	0x401107F0	SPCIF interrupt request register
SPCIF_INTR_SET	0x401107F4	SPCIF interrupt set request register
SPCIF_INTR_MASK	0x401107F8	SPCIF interrupt mask register
SPCIF_INTR_MASKED	0x401107FC	SPCIF interrupt masked request register

7.1.1 SPCIF_GEOMETRY

Flash/NVL geometry information

Address: 0x40110000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	W							
Name	FLASH [7:0]							
Bits	15	14	13	12	11	10	9	8
SW Access	R		R					
HW Access	W		W					
Name	SFLASH [15:14]		FLASH [13:8]					
Bits	23	22	21	20	19	18	17	16
SW Access	R		R		R			
HW Access	W		W		W			
Name	FLASH_ROW [23:22]		NUM_FLASH [21:20]		SFLASH [19:16]			
Bits	31	30	29	28	27	26	25	24
SW Access	RW		None					
HW Access			None					
Name	DE_CPD_LP		None [30:24]					

Bits	Name	Description
31	DE_CPD_LP	0': SRAM busy wait loop has not been copied. '1': Busy wait loop has been written into SRAM. Default Value: 0
23 : 22	FLASH_ROW	Page size in 64 Byte multiples (chip dependent): "0": 64 byte "1": 128 byte "2": 192 byte "3": 256 byte The page size is used to determine the number of Bytes in a page for Flash page based operations (e.g. PGM_PAGE). Note: the field name FLASH_ROW is misleading, as this field specifies the number of Bytes in a page, rather than the number of Bytes in a row. In a single plane flash macro architecture, a page consists of a single row. However, in a multi plane flash macro architecture, a page consists of multiple rows from different planes. Default Value: Undefined
21 : 20	NUM_FLASH	Number of flash macros (chip dependent): "0": 1 flash macro "1": 2 flash macros "2": 3 flash macros "3": 4 flash macros Default Value: Undefined

7.1.1 SPCIF_GEOMETRY (continued)

19 : 14	SFLASH	Supervisory flash capacity in 256 Byte multiples (chip dependent). If multiple flash macros are present, this field provides the supervisory flash capacity of all flash macros together: "0": 256 Bytes. "1": 2*256 Bytes. ... "63": 64*256 Bytes. Default Value: Undefined
13 : 0	FLASH	Regular flash capacity in 256 Byte multiples (chip dependent). If multiple flash macros are present, this field provides the flash capacity of all flash macros together: "0": 256 Bytes. "1": 2*256 Bytes. ... "16383": 16384*256 Bytes. Default Value: Undefined

7.1.2 SPCIF_INTR

SPCIF interrupt request register

Address: 0x401107F0

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW1C
HW Access	None							RW1S
Name	None [7:1]							TIMER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	TIMER	Timer counter value reaches "0". Set to '1', when event is detected. Write INTR field with '1', to clear bit. Write INTR_SET field with '1', to set bit. Default Value: 0

7.1.3 SPCIF_INTR_SET

SPCIF interrupt set request register

Address: 0x401107F4

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW1S
HW Access	None							A
Name	None [7:1]							TIMER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	TIMER	Write INTR_SET field with '1' to set corresponding INTR field. Default Value: 0

7.1.4 SPCIF_INTR_MASK

SPCIF interrupt mask register

Address: 0x401107F8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							RW
HW Access	None							R
Name	None [7:1]							TIMER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	TIMER	Mask for corresponding field in INTR register. Default Value: 0

7.1.5 SPCIF_INTR_MASKED

SPCIF interrupt masked request register

Address: 0x401107FC

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							R
HW Access	None							W
Name	None [7:1]							TIMER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	TIMER	Logical and of corresponding request and mask fields. Default Value: 0

Timer, Counter, PWM (TCPWM) registers

8 Timer, Counter, PWM (TCPWM) registers

This section discusses the TCPWM registers. It lists all the registers in mapping tables, in address order.

8.1 Register details

Register	Address	Description
TCPWM_CTRL	0x40200000	TCPWM control register 0.
TCPWM_CMD	0x40200008	TCPWM command register.
TCPWM_INTR_CAUSE	0x4020000C	TCPWM Counter interrupt cause register.
TCPWM_CNT0_CTRL	0x40200100	Counter control register
TCPWM_CNT0_STATUS	0x40200104	Counter status register
TCPWM_CNT0_COUNTER	0x40200108	Counter count register
TCPWM_CNT0_CC	0x4020010C	Counter compare/capture register
TCPWM_CNT0_CC_BUFF	0x40200110	Counter buffered compare/capture register
TCPWM_CNT0_PERIOD	0x40200114	Counter period register
TCPWM_CNT0_PERIOD_BUFF	0x40200118	Counter buffered period register
TCPWM_CNT0_TR_CTRL0	0x40200120	Counter trigger control register 0
TCPWM_CNT0_TR_CTRL1	0x40200124	Counter trigger control register 1
TCPWM_CNT0_TR_CTRL2	0x40200128	Counter trigger control register 2
TCPWM_CNT0_INTR	0x40200130	Interrupt request register.
TCPWM_CNT0_INTR_SET	0x40200134	Interrupt set request register.
TCPWM_CNT0_INTR_MASK	0x40200138	Interrupt mask register.
TCPWM_CNT0_INTR_MASKED	0x4020013C	Interrupt masked request register
TCPWM_CNT1_CTRL	0x40200140	Counter control register. See TCPWM_CNT0_CTRL for the details of bit fields.
TCPWM_CNT1_STATUS	0x40200144	Counter status register. See TCPWM_CNT0_STATUS for the details of bit fields.
TCPWM_CNT1_COUNTER	0x40200148	Counter count register. See TCPWM_CNT0_COUNTER for the details of bit fields.
TCPWM_CNT1_CC	0x4020014C	Counter compare/capture register. See TCPWM_CNT0_CC for the details of bit fields.
TCPWM_CNT1_CC_BUFF	0x40200150	Counter buffered compare/capture register. See TCPWM_CNT0_CC_BUFF for the details of bit fields.
TCPWM_CNT1_PERIOD	0x40200154	Counter period register. See TCPWM_CNT0_PERIOD for the details of bit fields.
TCPWM_CNT1_PERIOD_BUFF	0x40200158	Counter buffered period register. See TCPWM_CNT0_PERIOD_BUFF for the details of bit fields.
TCPWM_CNT1_TR_CTRL0	0x40200160	Counter trigger control register 0. See TCPWM_CNT0_TR_CTRL0 for the details of bit fields.
TCPWM_CNT1_TR_CTRL1	0x40200164	Counter trigger control register 1. See TCPWM_CNT0_TR_CTRL1 for the details of bit fields.

Timer, Counter, PWM (TCPWM) registers

Register	Address	Description
TCPWM_CNT1_TR_CTRL2	0x40200168	Counter trigger control register 2. See TCPWM_CNT0_TR_CTRL2 for the details of bit fields.
TCPWM_CNT1_INTR	0x40200170	Interrupt request register.. See TCPWM_CNT0_INTR for the details of bit fields.
TCPWM_CNT1_INTR_SET	0x40200174	Interrupt set request register.. See TCPWM_CNT0_INTR_SET for the details of bit fields.
TCPWM_CNT1_INTR_MASK	0x40200178	Interrupt mask register.. See TCPWM_CNT0_INTR_MASK for the details of bit fields.
TCPWM_CNT1_INTR_MASKED	0x4020017C	Interrupt masked request register. See TCPWM_CNT0_INTR_MASKED for the details of bit fields.

8.1.1 TCPWM_CTRL

TCPWM control register 0.

Address: 0x40200000

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW	
HW Access	None						R	
Name	None [7:2]						COUNTER_ENABLED [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1 : 0	COUNTER_ENABLED	Counter enables for counters 0 up to CNT_NR-1. '0': counter disabled. '1': counter enabled. Counter static configuration information (e.g. CTRL.MODE, all TR_CTRL0, TR_CTRL1, and TR_CTRL2 register fields) should only be modified when the counter is disabled. When a counter is disabled, command and status information associated to the counter is cleared by HW, this includes: - the associated counter triggers in the CMD register are set to '0'. - the counter's interrupt cause fields in counter's INTR register. - the counter's status fields in counter's STATUS register.. - the counter's trigger outputs ("tr_overflow", "tr_underflow" and "tr_compare_match"). - the counter's line outputs ("line_out" and "line_compl_out"). Default Value: 0

8.1.2 TCPWM_CMD

TCPWM command register.

Address: 0x40200008

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW1S	
HW Access	None						RW1C	
Name	None [7:2]						COUNTER_CAPTURE [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW1S	
HW Access	None						RW1C	
Name	None [15:10]						COUNTER_RELOAD [9:8]	

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW1S	
HW Access	None						RW1C	
Name	None [23:18]						COUNTER_STOP [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	None						RW1S	
HW Access	None						RW1C	
Name	None [31:26]						COUNTER_START [25:24]	

Bits	Name	Description
25 : 24	COUNTER_START	Counters SW start trigger. For HW behavior, see COUNTER_CAPTURE field. Default Value: 0
17 : 16	COUNTER_STOP	Counters SW stop trigger. For HW behavior, see COUNTER_CAPTURE field. Default Value: 0
9 : 8	COUNTER_RELOAD	Counters SW reload trigger. For HW behavior, see COUNTER_CAPTURE field. Default Value: 0
1 : 0	COUNTER_CAPTURE	Counters SW capture trigger. When written with '1', a capture trigger is generated and the HW sets the field to '0' when the SW trigger has taken effect. It should be noted that the HW operates on the counter frequency. If the counter is disabled through CTRL.COUNTER_ENABLED, the field is immediately set to '0'. Default Value: 0

8.1.3 TCPWM_INTR_CAUSE

TCPWM Counter interrupt cause register.

Address: 0x4020000C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						R	
HW Access	None						W	
Name	None [7:2]						COUNTER_INT [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1 : 0	COUNTER_INT	Counters interrupt signal active. If the counter is disabled through CTRL.COUNTER_ENABLED, the associated interrupt field is immediately set to '0'. Default Value: 0

8.1.4 TCPWM_CNT0_CTRL

Counter control register

Address: 0x40200100

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [7:4]				PW-M_STOP_ON_KILL	PWM_SYNC_KILL	AUTO_RELOAD_PERIOD	AUTO_RELOAD_CC

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	GENERIC [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None		RW		None	RW	RW	
HW Access	None		R		None	R	R	
Name	None [23:22]		QUADRATURE_MODE [21:20]		None	ONE_SHOT	UP_DOWN_MODE [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	None					RW		
HW Access	None					R		
Name	None [31:27]					MODE [26:24]		

Bits	Name	Description
26 : 24	MODE	Counter mode. Default Value: 0
		0x0: TIMER :
		Timer mode
		0x2: CAPTURE :
		Capture mode
		0x3: QUAD :
		Quadrature encoding mode
		0x4: PWM :
		Pulse width modulation (PWM) mode
		0x5: PWM_DT :
		PWM with deadtime insertion mode

8.1.4 TCPWM_CNT0_CTRL (continued)

0x6: PWM_PR :

Pseudo random pulse width modulation

21 : 20 QUADRATURE_MODE In QUAD mode selects quadrature encoding mode (X1/X2/X4).
In PWM, PWM_DT and PWM_PR modes, these two bits can be used to invert "dt_line_out" and "dt_line_compl_out". Inversion is the last step in generation of "dt_line_out" and "dt_line_compl_out"; i.e. a disabled output line "dt_line_out" has the value QUADRATURE_MODE[0] and a disabled output line "dt_line_compl_out" has the value QUADRATURE_MODE[1].
Default Value: 0

0x0: X1 :

X1 encoding (QUAD mode)

0x1: X2 :

X2 encoding (QUAD mode)

0x2: X4 :

X4 encoding (QUAD mode)

0x1: INV_OUT :

When bit 0 is '1', QUADRATURE_MODE[0] inverts "dt_line_out" (PWM/PWM_DT modes)

0x2: INV_COMPL_OUT :

When bit 1 is '1', QUADRATURE_MODE[1] inverts "dt_line_compl_out" (PWM/PWM_DT modes)

18 ONE_SHOT When '0', counter runs continuous. When '1', counter is turned off by hardware when a terminal count event is generated.
Default Value: 0

17 : 16 UP_DOWN_MODE Determines counter direction.
Default Value: 0

0x0: COUNT_UP :

Count up (to PERIOD). An overflow event is generated when the counter reaches PERIOD, and is changed to a different value. A terminal count event is generated when the counter reaches PERIOD, and is changed to a different value.

0x1: COUNT_DOWN :

Count down (to "0"). An underflow event is generated when the counter reaches "0", and is changed to a different value. A terminal count event is generated when the counter reaches "0", and is changed to a different value.

0x2: COUNT_UPDN1 :

Count up (to PERIOD), then count down (to "0"). An overflow event is generated when the counter reaches PERIOD, and is changed to a different value. An underflow event is generated when the counter reaches "0", and is changed to a different value. A terminal count event is generated when the counter reaches "0", and is changed to a different value.

8.1.4 TCPWM_CNT0_CTRL (continued)

0x3: COUNT_UPDN2 :

Count up (to PERIOD), then count down (to "0"). An overflow event is generated when the counter reaches PERIOD, and is changed to a different value. An underflow event is generated when the counter reaches "0", and is changed to a different value. A terminal count event is generated when the counter reaches "0", and is changed to a different value AND when the counter reaches PERIOD, and is changed to a different value. (this counter direction can be used for PWM functionality with asymmetrical updates).

15 : 8 GENERIC

Generic 8-bit control field. In PWM_DT mode, this field is used to determine the dead time: amount of dead time cycles in the counter clock domain. In all other modes, the lower 3 bits of this field determine pre-scaling of the selected counter clock.
Default Value: 0

0x0: DIVBY1 :

Divide by 1 (other-than-PWM_DT mode)

0x1: DIVBY2 :

Divide by 2 (other-than-PWM_DT mode)

0x2: DIVBY4 :

Divide by 4 (other-than-PWM_DT mode)

0x3: DIVBY8 :

Divide by 8 (other-than-PWM_DT mode)

0x4: DIVBY16 :

Divide by 16 (other-than-PWM_DT mode)

0x5: DIVBY32 :

Divide by 32 (other-than-PWM_DT mode)

0x6: DIVBY64 :

Divide by 64 (other-than-PWM_DT mode)

0x7: DIVBY128 :

Divide by 128 (other-than-PWM_DT mode)

3 PWM_STOP_ON_KILL

Specifies whether the counter stops on a kill events:
'0': kill event does NOT stop counter.
'1': kill event stops counter.

This field has a function in PWM, PWM_DT and PWM_PR modes only.
Default Value: 0

8.1.4 TCPWM_CNT0_CTRL (continued)

2	PWM_SYNC_KILL	Specifies asynchronous/synchronous kill behavior: '1': synchronous kill mode: the kill event disables the "dt_line_out" and "dt_line_compl_out" signals till the next terminal count event (synchronous kill). In synchronous kill mode, STOP_EDGE should be RISING_EDGE. '0': asynchronous kill mode: the kill event only disables the "dt_line_out" and "dt_line_compl_out" signals when present. In asynchronous kill mode, STOP_EDGE should be NO_EDGE_DET. This field has a function in PWM and PWM_DT modes only. This field is only used when PWM_STOP_ON_KILL is '0'. Default Value: 0
1	AUTO_RELOAD_PERIOD	Specifies switching of the PERIOD and buffered PERIOD values. This field has a function in PWM, PWM_DT and PWM_PR modes. '0': never switch. '1': switch on a terminal count event with an actively pending switch event. Default Value: 0
0	AUTO_RELOAD_CC	Specifies switching of the CC and buffered CC values. This field has a function in TIMER, PWM, PWM_DT and PWM_PR modes. Timer mode: '0': never switch. '1': switch on a compare match event. PWM, PWM_DT, PWM_PR modes: '0': never switch. '1': switch on a terminal count event with an actively pending switch event. Default Value: 0

8.1.5 TCPWM_CNT0_STATUS

Counter status register

Address: 0x40200104

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							R
HW Access	None							RW
Name	None [7:1]							DOWN

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	RW							
Name	GENERIC [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R	None						
HW Access	RW	None						
Name	RUNNING	None [30:24]						

Bits	Name	Description
31	RUNNING	When '0', the counter is NOT running. When '1', the counter is running. Default Value: 0
15 : 8	GENERIC	Generic 8-bit counter field. In PWM_DT mode, this counter is used for dead time insertion. In all other modes, this counter is used for pre-scaling the selected counter clock. PWM_DT mode can NOT use prescaled clock functionality. Default Value: 0
0	DOWN	When '0', counter is counting up. When '1', counter is counting down. In QUAD mode, this field indicates the direction of the latest counter change: '0' when last incremented and '1' when last decremented. Default Value: 0

8.1.6 TCPWM_CNT0_COUNTER

Counter count register

Address: 0x40200108

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	RW							
Name	COUNTER [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	COUNTER	16-bit counter value. It is advised to not write to this field when the counter is running. Default Value: 0

8.1.7 TCPWM_CNT0_CC

Counter compare/capture register

Address: 0x4020010C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	RW							
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	CC	In CAPTURE mode, captures the counter value. In other modes, compared to counter value. Default Value: 65535

8.1.8 TCPWM_CNT0_CC_BUFF

Counter buffered compare/capture register

Address: 0x40200110

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	RW							
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	CC	Additional buffer for counter CC register. Default Value: 65535

8.1.9 TCPWM_CNT0_PERIOD

Counter period register

Address: 0x40200114

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	RW							
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	PERIOD	Period value: upper value of the counter. When the counter should count for n cycles, this field should be set to n-1. Default Value: 65535

8.1.10 TCPWM_CNT0_PERIOD_BUFF

Counter buffered period register

Address: 0x40200118

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	RW							
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15 : 0	PERIOD	Additional buffer for counter PERIOD register. Default Value: 65535

8.1.11 TCPWM_CNT0_TR_CTRL0

Counter trigger control register 0

Address: 0x40200120

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	R				R			
Name	COUNT_SEL [7:4]				CAPTURE_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	RW				RW			
HW Access	R				R			
Name	STOP_SEL [15:12]				RELOAD_SEL [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	None				RW			
HW Access	None				R			
Name	None [23:20]				START_SEL [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
19 : 16	START_SEL	Selects one of the 16 input triggers as a start trigger. In QUAD mode, this is the second phase (phi B). Default Value: 0
15 : 12	STOP_SEL	Selects one of the 16 input triggers as a stop trigger. In PWM, PWM_DT and PWM_PR modes, this is the kill trigger. In these modes, the kill trigger is used to either temporarily block the PWM outputs (PWM_STOP_ON_KILL is '0') or stop the functionality (PWM_STOP_ON_KILL is '1'). For the PWM and PWM_DT modes, the blocking of the output signals can be asynchronous (STOP_EDGE should be NO_EDGE_DET) in which case the blocking is as long as the trigger is '1' or synchronous (STOP_EDGE should be RISING_EDGE) in which case it extends till the next terminal count event. Default Value: 0
11 : 8	RELOAD_SEL	Selects one of the 16 input triggers as a reload trigger. In QUAD mode, this is the index or revolution pulse. In this mode, it will update the counter with the value in the TCPWM_CNTn_PERIOD register. Default Value: 0
7 : 4	COUNT_SEL	Selects one of the 16 input triggers as a count trigger. In QUAD mode, this is the first phase (phi A). Default setting selects input trigger 1, which is always '1'. Default Value: 1
3 : 0	CAPTURE_SEL	Selects one of the 16 input triggers as a capture trigger. Input trigger 0 is always '0' and input trigger 1 is always '1'. Input trigger 2 is the first external trigger line (tcpwm.tr_in[0]). In the PWM, PWM_DT and PWM_PR modes this trigger is used to switch the values if the compare and period registers with their buffer counterparts. Default Value: 0

8.1.12 TCPWM_CNT0_TR_CTRL1 (continued)

8.1.12 TCPWM_CNT0_TR_CTRL1

Counter trigger control register 1

Address: 0x40200124

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		RW		RW		RW	
HW Access	R		R		R		R	
Name	STOP_EDGE [7:6]		RELOAD_EDGE [5:4]		COUNT_EDGE [3:2]		CAPTURE_EDGE [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	
HW Access	None						R	
Name	None [15:10]						START_EDGE [9:8]	

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9 : 8	START_EDGE	A start event will start the counter; i.e. the counter will become running. Starting does NOT enable the counter. A start event will not initialize the counter whereas the reload event does. Default Value: 3 0x0: RISING_EDGE : Rising edge. Any rising edge generates an event. 0x1: FALLING_EDGE : Falling edge. Any falling edge generates an event. 0x2: BOTH_EDGES : Rising AND falling edge. Any odd amount of edges generates an event. 0x3: NO_EDGE_DET : No edge detection, use trigger as is.
7 : 6	STOP_EDGE	A stop event, will stop the counter; i.e. it will no longer be running. Stopping will NOT disable the counter. Default Value: 3

0x0: RISING_EDGE :

Rising edge. Any rising edge generates an event.

0x1: FALLING_EDGE :

Falling edge. Any falling edge generates an event.

0x2: BOTH_EDGES :

Rising AND falling edge. Any odd amount of edges generates an event.

0x3: NO_EDGE_DET :

No edge detection, use trigger as is.

5 : 4 RELOAD_EDGE

A reload event will initialize the counter. When counting up, the counter is initialized to "0". When counting down, the counter is initialized with PERIOD.
Default Value: 3

0x0: RISING_EDGE :

Rising edge. Any rising edge generates an event.

0x1: FALLING_EDGE :

Falling edge. Any falling edge generates an event.

0x2: BOTH_EDGES :

Rising AND falling edge. Any odd amount of edges generates an event.

0x3: NO_EDGE_DET :

No edge detection, use trigger as is.

3 : 2 COUNT_EDGE

A counter event will increase or decrease the counter by '1'.
Default Value: 3

0x0: RISING_EDGE :

Rising edge. Any rising edge generates an event.

0x1: FALLING_EDGE :

Falling edge. Any falling edge generates an event.

0x2: BOTH_EDGES :

Rising AND falling edge. Any odd amount of edges generates an event.

0x3: NO_EDGE_DET :

No edge detection, use trigger as is.

1 : 0 CAPTURE_EDGE

A capture event will copy the counter value into the CC register.
Default Value: 3

0x0: RISING_EDGE :

Rising edge. Any rising edge generates an event.

8.1.12 TCPWM_CNT0_TR_CTRL1 (continued)

0x1: FALLING_EDGE :

Falling edge. Any falling edge generates an event.

0x2: BOTH_EDGES :

Rising AND falling edge. Any odd amount of edges generates an event.

0x3: NO_EDGE_DET :

No edge detection, use trigger as is.

8.1.13 TCPWM_CNT0_TR_CTRL2 (continued)

8.1.13 TCPWM_CNT0_TR_CTRL2

Counter trigger control register 2

Address: 0x40200128

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW		RW		RW	
HW Access	None		R		R		R	
Name	None [7:6]		UNDERFLOW_MODE [5:4]		OVERFLOW_MODE [3:2]		CC_MATCH_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
5 : 4	UNDERFLOW_MODE	Determines the effect of a counter underflow event (COUNTER reaches "0") on the "line_out" output signals. Default Value: 3 0x0: SET : Set to '1' 0x1: CLEAR : Set to '0' 0x2: INVERT : Invert 0x3: NO_CHANGE : No Change
3 : 2	OVERFLOW_MODE	Determines the effect of a counter overflow event (COUNTER reaches PERIOD) on the "line_out" output signals. Default Value: 3

0x0: SET :

Set to '1'

0x1: CLEAR :

Set to '0'

0x2: INVERT :

Invert

0x3: NO_CHANGE :

No Change

1 : 0 CC_MATCH_MODE

Determines the effect of a compare match event (COUNTER equals CC register) on the "line_out" output signals. Note that INVERT is especially useful for center aligned pulse width modulation.
To generate a duty cycle of 0%, the counter CC register should be set to "0". For a 100% duty cycle, the counter CC register should be set to larger than the counter PERIOD register.
Default Value: 3

0x0: SET :

Set to '1'

0x1: CLEAR :

Set to '0'

0x2: INVERT :

Invert

0x3: NO_CHANGE :

No Change

8.1.14 TCPWM_CNT0_INTR (continued)

8.1.14 TCPWM_CNT0_INTR

Interrupt request register.

Address: 0x40200130

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW1C	RW1C
HW Access	None						RW1S	RW1S
Name	None [7:2]						CC_MATCH	TC

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	CC_MATCH	Counter matches CC register event. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
0	TC	Terminal count event. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0

8.1.15 TCPWM_CNT0_INTR_SET

Interrupt set request register.

Address: 0x40200134

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW1S	RW1S
HW Access	None						A	A
Name	None [7:2]						CC_MATCH	TC

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	CC_MATCH	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	TC	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

8.1.16 TCPWM_CNT0_INTR_MASK

Interrupt mask register.

Address: 0x40200138

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [7:2]						CC_MATCH	TC

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	CC_MATCH	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	TC	Mask bit for corresponding bit in interrupt request register. Default Value: 0

8.1.17 TCPWM_CNT0_INTR_MASKED

Interrupt masked request register

Address: 0x4020013C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						R	R
HW Access	None						W	W
Name	None [7:2]						CC_MATCH	TC

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
1	CC_MATCH	Logical and of corresponding request and mask bits. Default Value: 0
0	TC	Logical and of corresponding request and mask bits. Default Value: 0

Serial Communication Block (SCB) registers

9 Serial Communication Block (SCB) registers

This section discusses the SCB registers. It lists all the registers in mapping tables, in address order.

9.1 Register details

Register	Address	Description
SCB0_CTRL	0x40240000	Generic control
SCB0_STATUS	0x40240004	Generic status
SCB0_SPI_CTRL	0x40240020	SPI control
SCB0_SPI_STATUS	0x40240024	SPI status
SCB0_SPI_TX_CTRL	0x40240028	SPI transmitter control
SCB0_SPI_RX_CTRL	0x4024002C	SPI receiver control
SCB0_UART_CTRL	0x40240040	UART control
SCB0_UART_TX_CTRL	0x40240044	UART transmitter control
SCB0_UART_RX_CTRL	0x40240048	UART receiver control
SCB0_UART_RX_STATUS	0x4024004C	UART receiver status
SCB0_UART_FLOW_CTRL	0x40240050	UART flow control
SCB0_I2C_CTRL	0x40240060	I2C control
SCB0_I2C_STATUS	0x40240064	I2C status
SCB0_I2C_M_CMD	0x40240068	I2C master command
SCB0_I2C_S_CMD	0x4024006C	I2C slave command
SCB0_I2C_CFG	0x40240070	I2C configuration
SCB0_I2C_STRETCH_CTRL	0x40240074	I2C stretch control
SCB0_I2C_STRETCH_STATUS	0x40240078	I2C stretch status
SCB0_TX_CTRL	0x40240200	Transmitter control
SCB0_TX_FIFO_CTRL	0x40240204	Transmitter FIFO control
SCB0_TX_FIFO_STATUS	0x40240208	Transmitter FIFO status
SCB0_TX_FIFO_WR	0x40240240	Transmitter FIFO write
SCB0_RX_CTRL	0x40240300	Receiver control
SCB0_RX_FIFO_CTRL	0x40240304	Receiver FIFO control
SCB0_RX_FIFO_STATUS	0x40240308	Receiver FIFO status
SCB0_RX_MATCH	0x40240310	Slave address and mask
SCB0_RX_FIFO_RD	0x40240340	Receiver FIFO read
SCB0_RX_FIFO_RD_SILENT	0x40240344	Receiver FIFO read silent
SCB0_EZ_DATA0	0x40240400	Memory buffer
SCB0_EZ_DATA1	0x40240404	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA2	0x40240408	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.

Serial Communication Block (SCB) registers

Register	Address	Description
SCB0_EZ_DATA3	0x4024040C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA4	0x40240410	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA5	0x40240414	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA6	0x40240418	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA7	0x4024041C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA8	0x40240420	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA9	0x40240424	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA10	0x40240428	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA11	0x4024042C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA12	0x40240430	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA13	0x40240434	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA14	0x40240438	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA15	0x4024043C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA16	0x40240440	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA17	0x40240444	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA18	0x40240448	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA19	0x4024044C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA20	0x40240450	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA21	0x40240454	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA22	0x40240458	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA23	0x4024045C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.

Serial Communication Block (SCB) registers

Register	Address	Description
SCB0_EZ_DATA24	0x40240460	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA25	0x40240464	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA26	0x40240468	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA27	0x4024046C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA28	0x40240470	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA29	0x40240474	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA30	0x40240478	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_EZ_DATA31	0x4024047C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB0_INTR_CAUSE	0x40240E00	Active clocked interrupt signal
SCB0_INTR_I2C_EC	0x40240E80	Externally clocked I2C interrupt request
SCB0_INTR_I2C_EC_MASK	0x40240E88	Externally clocked I2C interrupt mask
SCB0_INTR_I2C_EC_MASKED	0x40240E8C	Externally clocked I2C interrupt masked
SCB0_INTR_SPI_EC	0x40240EC0	Externally clocked SPI interrupt request
SCB0_INTR_SPI_EC_MASK	0x40240EC8	Externally clocked SPI interrupt mask
SCB0_INTR_SPI_EC_MASKED	0x40240ECC	Externally clocked SPI interrupt masked
SCB0_INTR_M	0x40240F00	Master interrupt request
SCB0_INTR_M_SET	0x40240F04	Master interrupt set request
SCB0_INTR_M_MASK	0x40240F08	Master interrupt mask
SCB0_INTR_M_MASKED	0x40240F0C	Master interrupt masked request
SCB0_INTR_S	0x40240F40	Slave interrupt request
SCB0_INTR_S_SET	0x40240F44	Slave interrupt set request
SCB0_INTR_S_MASK	0x40240F48	Slave interrupt mask
SCB0_INTR_S_MASKED	0x40240F4C	Slave interrupt masked request
SCB0_INTR_TX	0x40240F80	Transmitter interrupt request
SCB0_INTR_TX_SET	0x40240F84	Transmitter interrupt set request
SCB0_INTR_TX_MASK	0x40240F88	Transmitter interrupt mask
SCB0_INTR_TX_MASKED	0x40240F8C	Transmitter interrupt masked request
SCB0_INTR_RX	0x40240FC0	Receiver interrupt request
SCB0_INTR_RX_SET	0x40240FC4	Receiver interrupt set request
SCB0_INTR_RX_MASK	0x40240FC8	Receiver interrupt mask
SCB0_INTR_RX_MASKED	0x40240FCC	Receiver interrupt masked request

Serial Communication Block (SCB) registers

Register	Address	Description
SCB1_CTRL	0x40250000	Generic control. See SCB0_CTRL for the details of bit fields.
SCB1_STATUS	0x40250004	Generic status. See SCB0_STATUS for the details of bit fields.
SCB1_I2C_CTRL	0x40250060	I2C control. See SCB0_I2C_CTRL for the details of bit fields.
SCB1_I2C_STATUS	0x40250064	I2C status. See SCB0_I2C_STATUS for the details of bit fields.
SCB1_I2C_M_CMD	0x40250068	I2C master command. See SCB0_I2C_M_CMD for the details of bit fields.
SCB1_I2C_S_CMD	0x4025006C	I2C slave command. See SCB0_I2C_S_CMD for the details of bit fields.
SCB1_I2C_CFG	0x40250070	I2C configuration. See SCB0_I2C_CFG for the details of bit fields.
SCB1_I2C_STRETCH_CTRL	0x40250074	I2C stretch control. See SCB0_I2C_STRETCH_CTRL for the details of bit fields.
SCB1_I2C_STRETCH_STATUS	0x40250078	I2C stretch status. See SCB0_I2C_STRETCH_STATUS for the details of bit fields.
SCB1_TX_CTRL	0x40250200	Transmitter control. See SCB0_TX_CTRL for the details of bit fields.
SCB1_TX_FIFO_CTRL	0x40250204	Transmitter FIFO control. See SCB0_TX_FIFO_CTRL for the details of bit fields.
SCB1_TX_FIFO_STATUS	0x40250208	Transmitter FIFO status. See SCB0_TX_FIFO_STATUS for the details of bit fields.
SCB1_TX_FIFO_WR	0x40250240	Transmitter FIFO write. See SCB0_TX_FIFO_WR for the details of bit fields.
SCB1_RX_CTRL	0x40250300	Receiver control. See SCB0_RX_CTRL for the details of bit fields.
SCB1_RX_FIFO_CTRL	0x40250304	Receiver FIFO control. See SCB0_RX_FIFO_CTRL for the details of bit fields.
SCB1_RX_FIFO_STATUS	0x40250308	Receiver FIFO status. See SCB0_RX_FIFO_STATUS for the details of bit fields.
SCB1_RX_MATCH	0x40250310	Slave address and mask. See SCB0_RX_MATCH for the details of bit fields.
SCB1_RX_FIFO_RD	0x40250340	Receiver FIFO read. See SCB0_RX_FIFO_RD for the details of bit fields.
SCB1_RX_FIFO_RD_SILENT	0x40250344	Receiver FIFO read silent. See SCB0_RX_FIFO_RD_SILENT for the details of bit fields.
SCB1_EZ_DATA0	0x40250400	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA1	0x40250404	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.

Serial Communication Block (SCB) registers

Register	Address	Description
SCB1_EZ_DATA2	0x40250408	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA3	0x4025040C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA4	0x40250410	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA5	0x40250414	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA6	0x40250418	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA7	0x4025041C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA8	0x40250420	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA9	0x40250424	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA10	0x40250428	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA11	0x4025042C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA12	0x40250430	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA13	0x40250434	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA14	0x40250438	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA15	0x4025043C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA16	0x40250440	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA17	0x40250444	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA18	0x40250448	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA19	0x4025044C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA20	0x40250450	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA21	0x40250454	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA22	0x40250458	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.

Serial Communication Block (SCB) registers

Register	Address	Description
SCB1_EZ_DATA23	0x4025045C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA24	0x40250460	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA25	0x40250464	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA26	0x40250468	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA27	0x4025046C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA28	0x40250470	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA29	0x40250474	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA30	0x40250478	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_EZ_DATA31	0x4025047C	Memory buffer. See SCB0_EZ_DATA0 for the details of bit fields.
SCB1_INTR_CAUSE	0x40250E00	Active clocked interrupt signal
SCB1_INTR_I2C_EC	0x40250E80	Externally clocked I2C interrupt request. See SCB0_INTR_I2C_EC for the details of bit fields.
SCB1_INTR_I2C_EC_MASK	0x40250E88	Externally clocked I2C interrupt mask. See SCB0_INTR_I2C_EC_MASK for the details of bit fields.
SCB1_INTR_I2C_EC_MASKED	0x40250E8C	Externally clocked I2C interrupt masked. See SCB0_INTR_I2C_EC_MASKED for the details of bit fields.
SCB1_INTR_M	0x40250F00	Master interrupt request
SCB1_INTR_M_SET	0x40250F04	Master interrupt set request
SCB1_INTR_M_MASK	0x40250F08	Master interrupt mask
SCB1_INTR_M_MASKED	0x40250F0C	Master interrupt masked request
SCB1_INTR_S	0x40250F40	Slave interrupt request
SCB1_INTR_S_SET	0x40250F44	Slave interrupt set request
SCB1_INTR_S_MASK	0x40250F48	Slave interrupt mask
SCB1_INTR_S_MASKED	0x40250F4C	Slave interrupt masked request
SCB1_INTR_TX	0x40250F80	Transmitter interrupt request
SCB1_INTR_TX_SET	0x40250F84	Transmitter interrupt set request
SCB1_INTR_TX_MASK	0x40250F88	Transmitter interrupt mask
SCB1_INTR_TX_MASKED	0x40250F8C	Transmitter interrupt masked request
SCB1_INTR_RX	0x40250FC0	Receiver interrupt request
SCB1_INTR_RX_SET	0x40250FC4	Receiver interrupt set request
SCB1_INTR_RX_MASK	0x40250FC8	Receiver interrupt mask
SCB1_INTR_RX_MASKED	0x40250FCC	Receiver interrupt masked request

9.1.1 SCB0_CTRL

Generic control

Address: 0x40240000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				OVS [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	RW		None			RW	RW	RW
HW Access	R		None			R	R	R
Name	MEM_WIDTH [15:14]		None [13:11]			EZ_MODE	EC_OP_- MODE	EC_AM_- MODE

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [23:18]						BLOCK	ADDR_AC- CEPT

Bits	31	30	29	28	27	26	25	24
SW Access	RW	None		RW	None		RW	
HW Access	R	None		R	None		R	
Name	ENABLED	None [30:29]		EC_AC- CESS	None [27:26]		MODE [25:24]	

Bits	Name	Description
31	ENABLED	SCB block is enabled ('1') or not ('0'). The proper order in which to initialize SCB is as follows: - Program protocol specific information using SPI_CTRL, UART_CTRL (and UART_TX_CTRL and UART_RX_CTRL) or I2C_CTRL registers. This includes selection of a submode, master/slave functionality and transmitter/receiver functionality when applicable. - Program generic transmitter (TX_CTRL) and receiver (RX_CTRL) information. This includes enabling of the transmitter and receiver functionality. - Program transmitter FIFO (TX_FIFO_CTRL) and receiver FIFO (RX_FIFO_CTRL) information. - Program CTRL register to enable SCB, select the specific operation mode and oversampling factor. Generally when this block is enabled, no control information should be changed. Changes should be made AFTER disabling this block, e.g. to modify the operation mode (from I2C to SPI) or to go from externally to internally clocked. The change takes effect after the block is re-enabled. Note that disabling the block will cause re-initialization of the design and associated state is lost (e.g. FIFO content). Specific to SPI master case, when SCB is idle, below registers can be changed without disabling SCB block, TX_CTRL TX_FIFO_CTRL RX_CTRL RX_FIFO_CTRL SPI_CTRL.SSEL, Default Value: 0

9.1.1 SCB0_CTRL (continued)

28	EC_ACCESS	EC_ACCESS is used to enable I2CS_EC or SPIS_EC access to internal EZ memory. 1: enable clk_scb 0: disable clk_scb Before going to deepsleep this field should be set to 1. when waking up from DeepSleep power mode, and PLL is locked (clk_scb is at expected frequency), this field should be set to 0. Default Value: 0
25 : 24	MODE	Mode of operation (3: Reserved) Default Value: 3 0x0: I2C : Inter-Integrated Circuits (I2C) mode. 0x1: SPI : Serial Peripheral Interface (SPI) mode. 0x2: UART : Universal Asynchronous Receiver/Transmitter (UART) mode.
17	BLOCK	Only used in externally clocked mode. If the externally clocked logic and the internal CPU accesses to EZ memory coincide/collide, this bit determines whether the CPU access should block and result in bus wait states ('BLOCK is 1') or not ('BLOCK is 0'). IF BLOCK is '0' and the accesses collide, CPU read operations return 0xffff:ffff and CPU write operations are ignored. Colliding accesses are registered as interrupt causes: INTR_TX.BLOCKED and INTR_RX.BLOCKED. Default Value: 0
16	ADDR_ACCEPT	Determines whether a received matching address is accepted in the RX FIFO ('1') or not ('0'). In I2C mode, this field is used to allow the slave to put the received slave address or general call address in the RX FIFO. Note that a received matching address is put in the RX FIFO when this bit is '1' for both I2C read and write transfers. In multi-processor UART receiver mode, this field is used to allow the receiver to put the received address in the RX FIFO. Note: non-matching addresses are never put in the RX FIFO. Default Value: 0
15 : 14	MEM_WIDTH	Determines the number of bits per FIFO data element, depending on physical SRAM cell data width. On M0S8/MXS40S platform, the SRAM data width is 16 bit, so WORD (2) is not supported. On MXS40E platform, the SRAM data width is 32 bits. Default Value: 1 0x0: BYTE : 8-bit FIFO data elements. This mode provides the biggest amount of FIFO entries, but TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH are restricted to [0, 7]. 0x1: HALFWORD : 16-bit FIFO data elements. TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH are restricted to [0, 15]. 0x2: WORD : 32-bit FIFO data elements. This mode provides the smallest amount of FIFO entries, but TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH can be in a range of [0, 31].

9.1.1 SCB0_CTRL (continued)

0x3: Reserved :

This setting is reserved. Do not use.

10	EZ_MODE	Non EZ mode ('0') or EZ mode ('1'). In EZ mode, a meta protocol is applied to the serial interface protocol. This meta protocol adds meaning to the data frames transferred by the serial interface protocol: a data frame can represent a memory address, a write memory data element or a read memory data element. EZ mode is only used for synchronous serial interface protocols: SPI and I2C. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported and the transmitter should use continuous data frames; i.e. data frames not separated by slave deselection. This mode is only applicable to slave functionality. In EZ mode, the slave can read from and write to an addressable memory structure of 32 bytes. In EZ mode, data frames should 8-bit in size and should be transmitted and received with the Most Significant Bit (MSB) first. In UART mode this field should be '0'. Default Value: 0
9	EC_OP_MODE	This field specifies the clocking for the SCB block '0': Internally clocked mode '1': externally clocked mode In internally clocked mode, the serial interface protocols run off the SCB clock. In externally clocked mode, the serial interface protocols run off the clock as provided by the serial interface. Externally clocked operation mode is only used for synchronous serial interface protocols (SPI and I2C) in slave mode AND EZ mode. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported. The maximum SPI slave, EZ mode bitrate is 48 Mbps (transmission and IO delays outside the IP will degrade the effective bitrate). In UART mode this field should be '0'. Default Value: 0
8	EC_AM_MODE	This field specifies the clocking for the address matching (I2C) or slave selection detection logic (SPI) '0': Internally clocked mode '1': Externally clocked mode In internally clocked mode, the serial interface protocols run off the SCB clock. In externally clocked mode, the serial interface protocols run off the clock as provided by the serial interface. The clocking for the rest of the logic is determined by CTRL.EC_OP_MODE. Externally clocked mode is only used for synchronous serial interface protocols (SPI and I2C) in slave mode. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported. In UART mode this field should be '0'. Default Value: 0

9.1.1 SCB0_CTRL (continued)

3 : 0 OVS

Serial interface bit period oversampling factor expressed in SCB clock cycles. Used for SPI and UART functionality. $OVS + 1$ SCB clock cycles constitute a single serial interface clock/bit cycle. This field is NOT used in externally clocked mode. If OVS is odd, the oversampling factor is even and the low and high phase of the interface clock period are the same. If OVS is even, the oversampling factor is odd and the low and high phase can differ by 1 SCB clock period.

In SPI master mode, the valid range is [3, 15]. At an SCB frequency of 48 MHz, the maximum SPI bit rate is 12 Mbps, assuming ideal (0 ns) IO cell and routing (chip and board) delay. The calculated maximum bit rate decreases, when realistic chip and routing delays are taken into account. The effective system bit rate is dependent on the external SPI slave that we communicate with. If the SPI output clock to SPI MISO input round trip delay is significant (multiple SPI output clock cycles), it may be necessary to increase OVS and/or to set SPI_CTRL.LATE_MISO_SAMPLE to '1' to achieve the maximum possible system bit rate.

In SPI slave mode, the OVS field is NOT used. However, there is a frequency requirement for the SCB clock wrt. the SPI input clock (IF) on the interface to guarantee functional correct behavior. This requirement is expressed as a ratio: SCB clock/IF clock. The ratio is dependent on the setting of RX_CTRL.MEDIAN and the external SPI master's capability to support "late MISO sample" functionality (similar to our SPI master functionality represented by SPI_CTRL.LATE_MISO_SAMPLE):

- MEDIAN is '0' and external SPI master has NO "late MISO sample functionality": SCB clock/IF clock ≥ 6 . At a SCB frequency of 48 MHz, the maximum bit rate is 8 Mbps.
- MEDIAN is '0' and external SPI master has "late MISO sample functionality": SCB clock/IF clock ≥ 3 . At a SCB frequency of 48 MHz, the maximum bit rate is 16 Mbps.
- MEDIAN is '1' and external SPI master has NO "late MISO sample functionality": SCB clock/IF clock ≥ 8 . At a SCB frequency of 48 MHz, the maximum bit rate is 6 Mbps.
- MEDIAN is '1' and external SPI master has "late MISO sample functionality": SCB clock/IF clock ≥ 4 . At a SCB frequency of 48 MHz, the maximum bit rate is 12 Mbps.

As discussed earlier, the calculated maximum bit rate decreases, when realistic chip and routing delays are taken into account.

In UART standard submode (including LIN), the valid range is [7, 15]. In UART SmartCard submode, the valid range is [7, 15].

In UART TX IrDA submode this field indirectly specifies the oversampling. The oversampling determines the interface clock/bit cycle and the width of the pulse. Only normal transmission mode is supported, the pulse is roughly 3/16 of the bit period (for all bit rates). There is only one valid OVS value:

- 0: 16 times oversampling.
SCB clock frequency of 16×115.2 KHz for 115.2 Kbps.
SCB clock frequency of 16×57.6 KHz for 57.6 Kbps.
SCB clock frequency of 16×38.4 KHz for 38.4 Kbps.
SCB clock frequency of 16×19.2 KHz for 19.2 Kbps.
SCB clock frequency of 16×9.6 KHz for 9.6 Kbps.
SCB clock frequency of 16×2.4 KHz for 2.4 Kbps.
SCB clock frequency of 16×1.2 KHz for 1.2 Kbps.
- all other values are not used in normal mode.

In UART RX IrDA submode (1.2, 2.4, 9.6, 19.2, 38.4, 57.6 and 115.2 Kbps) this field indirectly specifies the oversampling. The oversampling determines the interface clock/bit cycle and the width of the pulse. In normal transmission mode, this pulse is roughly 3/16 of the bit period (for all bit rates). In low power transmission mode, this pulse is potentially smaller (down to 1.62 us typical and 1.41 us minimal) than 3/16 of the bit period (for < 115.2 Kbps bitrates). Pulse widths greater or equal than two SCB clock cycles are guaranteed to be detected by the receiver. Pulse widths less than two SCB clock cycles and greater or equal than one SCB clock cycle may be detected by the receiver. Pulse widths less than one SCB clock cycle will not be detected by the receiver. RX_CTRL.MEDIAN should be set to '1' for IrDA receiver functionality. The SCB clock (as provided by the programmable clock block) and the oversampling together determine the IrDA bitrate. Normal mode, OVS field values (with the required SCB clock frequency):

- 0: 16 times oversampling.
SCB clock frequency of 16×115.2 KHz for 115.2 Kbps.
SCB clock frequency of 16×57.6 KHz for 57.6 Kbps.
SCB clock frequency of 16×38.4 KHz for 38.4 Kbps.
SCB clock frequency of 16×19.2 KHz for 19.2 Kbps.
SCB clock frequency of 16×9.6 KHz for 9.6 Kbps.
SCB clock frequency of 16×2.4 KHz for 2.4 Kbps.
SCB clock frequency of 16×1.2 KHz for 1.2 Kbps.
- all other values are not used in normal mode.

Low power mode, OVS field values (with the required SCB clock frequency):

- 0: 16 times oversampling.
SCB clock frequency of 16×115.2 KHz for 115.2 Kbps.
- 1: 32 times oversampling.
SCB clock frequency of 32×57.6 KHz for 57.6 Kbps.
- 2: 48 times oversampling.
SCB clock frequency of 48×38.4 KHz for 38.4 Kbps.
- 3: 96 times oversampling.
SCB clock frequency of 96×19.2 KHz for 19.2 Kbps.
- 4: 192 times oversampling.
SCB clock frequency of 192×9.6 KHz for 9.6 Kbps.
- 5: 768 times oversampling.
SCB clock frequency of 768×2.4 KHz for 2.4 Kbps.
- 6: 1536 times oversampling.
SCB clock frequency of 1536×1.2 KHz for 1.2 Kbps.
- all other values are not used in low power mode.

Default Value: 15

9.1.2 SCB0_STATUS

Generic status

Address: 0x40240004

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							R
HW Access	None							W
Name	None [7:1]							EC_BUSY

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
0	EC_BUSY	Indicates whether the externally clocked logic is potentially accessing the EZ memory (this is only possible in EZ mode). This bit can be used by SW to determine whether it is safe to issue a SW access to the EZ memory (without bus wait states (a blocked SW access) or bus errors being generated). Note that the INTR_TX.BLOCKED and INTR_RX.BLOCKED interrupt causes are used to indicate whether a SW access was actually blocked by externally clocked logic. Default Value: Undefined

9.1.3 SCB0_SPI_CTRL

SPI control

Address: 0x40240020

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	RW	RW	RW	RW
HW Access	None		R	R	R	R	R	R
Name	None [7:6]		SCLK_- CONTINU- OUS	LATE_MISO _SAMPLE	CPOL	CPHA	SE- LECT_PRE- CEDE	SSEL_- CONTINU- OUS

Bits	15	14	13	12	11	10	9	8
SW Access	None	RW	RW	RW	RW	RW	RW	RW
HW Access	None	R	R	R	R	R	R	R
Name	None	SSEL_INTE R_- FRAME_DE L	SSEL_HOL D_DEL	SSEL_SET- UP_DEL	SSEL_PO- LARITY3	SSEL_PO- LARITY2	SSEL_PO- LARITY1	SSEL_PO- LARITY0

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							LOOPBACK

Bits	31	30	29	28	27	26	25	24
SW Access	RW	None			RW		RW	
HW Access	R	None			R		R	
Name	MASTER_- MODE	None [30:28]			SSEL [27:26]		MODE [25:24]	

Bits	Name	Description
31	MASTER_MODE	Master ('1') or slave ('0') mode. In master mode, transmission will commence on availability of data frames in the TX FIFO. In slave mode, when selected and there is no data frame in the TX FIFO, the slave will transmit all '1's. In both master and slave modes, received data frames will be lost if the RX FIFO is full. Default Value: 0
27 : 26	SSEL	Selects one of the four incoming/outgoing SPI slave select signals: - 0: Slave 0, SSEL[0]. - 1: Slave 1, SSEL[1]. - 2: Slave 2, SSEL[2]. - 3: Slave 3, SSEL[3]. SCB block should be disabled when changes are made to this field. Default Value: 0
25 : 24	MODE	Submode of SPI operation (3: Reserved). Default Value: 3

9.1.3 SCB0_SPI_CTRL (continued)

0x0: SPI_MOTOROLA :

SPI Motorola submode. In master mode, when not transmitting data (Slave SELECT is inactive), SCLK is stable at CPOL. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), Slave SELECT is inactive.

0x1: SPI_TI :

SPI Texas Instruments submode. In master mode, when not transmitting data, SCLK is stable at '0'. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), Slave SELECT is inactive; i.e. no pulse is generated.

0x2: SPI_NS :

SPI National Semiconductors submode. In master mode, when not transmitting data, SCLK is stable at '0'. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), Slave SELECT is inactive.

16	LOOPBACK	Local loopback control (does NOT affect the information on the pins). Only used in master mode. Not used in National Semiconductors submode. '0': No local loopback '1': the SPI master MISO line is connected to the SPI master MOSI line. In other words, in loop-back mode the SPI master receives on MISO what it transmits on MOSI. Default Value: 0
14	SSEL_INTER_- FRAME_DEL	Indicates the SPI SELECT inter-dataframe delay (between SELECT deactivation and SELECT activation). '0': 1.5 SPI clock cycles '1': 2.5 SPI clock cycles Only applies in SPI MOTOROLA submode and when SPI_CTRL.SSEL_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle. Default Value: 0
13	SSEL_HOLD_DEL	Indicates the SPI SELECT hold delay (between SPI clock edge to sample the last MOSI bit, and SELECT deactivation). '0': 0.75 SPI clock cycles '1': 1.75 SPI clock cycles Only applies in SPI MOTOROLA submode and when SCLK_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle. Default Value: 0
12	SSEL_SETUP_DEL	Indicates the SPI SELECT setup delay (between SELECT activation and SCLK clock edge to sample the first MOSI bit). '0': 0.75 SPI clock cycles '1': 1.75 SPI clock cycles Only applies in SPI MOTOROLA submode and when SCLK_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle. Default Value: 0
11	SSEL_POLARITY3	Slave select polarity. Default Value: 0
10	SSEL_POLARITY2	Slave select polarity. Default Value: 0
9	SSEL_POLARITY1	Slave select polarity. Default Value: 0

9.1.3 SCB0_SPI_CTRL (continued)

8	SSEL_POLARITY0	Slave select polarity. SSEL_POLARITY0 applies to the outgoing SPI slave select signal 0 (master mode) and to the incoming SPI slave select signal (slave mode). For Motorola and National Semiconductors submodes: '0': slave select is low/'0' active. '1': slave select is high/'1' active. For Texas Instruments submode: '0': high/'1' active precede/coincide pulse. '1': low/'0' active precede/coincide pulse. Default Value: 0
5	SCLK_CONTINUOUS	Only applicable in master mode. '0': SCLK is generated, when the SPI master is enabled and data is transmitted. '1': SCLK is generated, when the SPI master is enabled. This mode is useful for slave devices that use SCLK for functional operation other than just SPI functionality. Default Value: 0
4	LATE_MISO_SAMPLE	Changes the SCLK edge on which MISO is captured. Only used in master mode. When '0', the default applies (for Motorola as determined by CPOL and CPHA, for Texas Instruments on the falling edge of SCLK and for National Semiconductors on the rising edge of SCLK). When '1', the alternate clock edge is used (which comes half a SPI SCLK period later). Late sampling addresses the round trip delay associated with transmitting SCLK from the master to the slave and transmitting MISO from the slave to the master. Default Value: 1
3	CPOL	Indicates the clock polarity. This field, together with the CPHA field, indicates when MOSI data is driven and MISO data is captured: - CPOL is '0': SCLK is '0' when not transmitting data. - CPOL is '1': SCLK is '1' when not transmitting data. Default Value: 0
2	CPHA	Indicates the clock phase. This field, together with the CPOL field, indicates when MOSI data is driven and MISO data is captured: - Motorola mode 0. CPOL is '0', CPHA is '0': MOSI is driven on a falling edge of SCLK. MISO is captured on a rising edge of SCLK. - Motorola mode 1. CPOL is '0', CPHA is '1': MOSI is driven on a rising edge of SCLK. MISO is captured on a falling edge of SCLK. - Motorola mode 2. CPOL is '1', CPHA is '0': MOSI is driven on a rising edge of SCLK. MISO is captured on a falling edge of SCLK. - Motorola mode 3. CPOL is '1', CPHA is '1': MOSI is driven on a falling edge of SCLK. MISO is captured on a rising edge of SCLK. In SPI Motorola submode, all four CPOL/CPHA modes are valid. in SPI NS submode, only CPOL=0 CPHA=0 mode is valid. in SPI TI submode, only CPOL=0 CPHA=1 mode is valid. Default Value: 0
1	SELECT_PRECEDE	Only used in SPI Texas Instruments' submode. When '1', the data frame start indication is a pulse on the Slave SELECT line that precedes the transfer of the first data frame bit. When '0', the data frame start indication is a pulse on the Slave SELECT line that coincides with the transfer of the first data frame bit. Default Value: 0

9.1.3 SCB0_SPI_CTRL (continued)

0	SSEL_CONTINUOUS	Continuous SPI data transfers enabled ('1') or not ('0'). This field is used in master mode. In slave mode, both continuous and non-continuous SPI data transfers are supported independent of this field. When continuous transfers are enabled individual data frame transfers are not necessarily separated by slave deselection (as indicated by the level or pulse on the SELECT line): if the TX FIFO has multiple data frames, data frames are send out without slave deselection. When continuous transfers are not enabled individual data frame transfers are always separated by slave deselection: independent of the availability of TX FIFO data frames, data frames are sent out with slave deselection. Default Value: 0
---	-----------------	--

9.1.4 SCB0_SPI_STATUS

SPI status

Address: 0x40240024

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						R	R
HW Access	None						W	W
Name	None [7:2]						SPI_EC_BUSY	BUS_BUSY

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	W							
Name	CURR_EZ_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	W							
Name	BASE_EZ_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 16	BASE_EZ_ADDR	SPI base EZ address. Address as provided by a SPI write transfer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable, as clock domain synchronization is not performed in the design. Default Value: Undefined
15 : 8	CURR_EZ_ADDR	SPI current EZ address. Current address pointer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable (during an ongoing transfer when SPI_EC_BUSY is '1'), as clock domain synchronization is not performed in the design. Default Value: Undefined
1	SPI_EC_BUSY	Indicates whether the externally clocked logic is potentially accessing the EZ memory and/or updating BASE_ADDR or CURR_ADDR (this is only possible in EZ mode). This bit can be used by SW to determine whether BASE_ADDR and CURR_ADDR are reliable. Default Value: Undefined
0	BUS_BUSY	SPI bus is busy. The bus is considered busy ('1') during an ongoing transaction. For Motorola and National submodes, the busy bit is '1', when the slave selection is activated. For TI submode, the busy bit is '1' from the time the preceding/coinciding slave select is activated for the first transmitted data frame, till the last MOSI/MISO bit of the last data frame is transmitted. Default Value: Undefined

9.1.5 SCB0_SPI_TX_CTRL

SPI transmitter control

Address: 0x40240028

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	None			
HW Access	None		R	R	None			
Name	None [7:6]		PARITY_ENABLED	PARITY	None			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							MOSI_IDLE_HIGH

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	MOSI_IDLE_HIGH	SPI master MOSI output level when SELECT output inactive, 0: retain the level of last data bit 1: change to high, (MOSI level is high, before the first data bit time, and after data bit time, defined SSEL/SCLK driving edge with CPOL/CPHA) Default Value: 0
5	PARITY_ENABLED	Parity generation enabled ('1') or not ('0'). Default Value: 0
4	PARITY	Parity bit. When '0', the transmitter generates an even parity. When '1', the transmitter generates an odd parity. Default Value: 0

9.1.6 SCB0_SPI_RX_CTRL

SPI receiver control

Address: 0x4024002C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	None			
HW Access	None		R	R	None			
Name	None [7:6]		PARITY_ENABLED	PARITY	None			

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							DROP_ON_PARITY_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	DROP_ON_PARITY_ERROR	Behavior when a parity check fails. When '0', received data is send to the RX FIFO. When '1', received data is dropped and lost. Default Value: 0
5	PARITY_ENABLED	Parity checking enabled ('1') or not ('0'). Default Value: 0
4	PARITY	Parity bit. When '0', the receiver expects an even parity. When '1', the receiver expects an odd parity. Default Value: 0

9.1.7 SCB0_UART_CTRL

UART control

Address: 0x40240040

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							LOOPBACK
Bits	31	30	29	28	27	26	25	24
SW Access	None						RW	
HW Access	None						R	
Name	None [31:26]						MODE [25:24]	

Bits	Name	Description
25 : 24	MODE	Submode of UART operation (3: Reserved) Default Value: 3 0x0: UART_STD : Standard UART submode. 0x1: UART_SMARTCARD : SmartCard (ISO7816) submode. Support for negative acknowledgement (NACK) on the receiver side and retransmission on the transmitter side. 0x2: UART_IRDA : Infrared Data Association (IrDA) submode. Return to Zero modulation scheme. In this mode, the oversampling factor should be 16, that is OVS should be set to 15.
16	LOOPBACK	Local loopback control (does NOT affect the information on the pins). 0: Loopback is not enabled 1: UART_TX is connected to UART_RX. UART_RTS is connected to UART_CTS. This allows a SCB UART transmitter to communicate with its receiver counterpart. Default Value: 0

9.1.8 SCB0_UART_TX_CTRL

UART transmitter control

Address: 0x40240044

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		RW	RW	None	RW		
HW Access	None		R	R	None	R		
Name	None [7:6]		PARITY_ENABLED	PARITY	None	STOP_BITS [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							RETRY_ON_NACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	RETRY_ON_NACK	When '1', a data frame is retransmitted when a negative acknowledgement is received. Only applicable to the SmartCard submode. Default Value: 0
5	PARITY_ENABLED	Parity generation enabled ('1') or not ('0'). Only applicable in standard UART submodes. In SmartCard submode, parity generation is always enabled through hardware. In IrDA submode, parity generation is always disabled through hardware Default Value: 0
4	PARITY	Parity bit. When '0', the transmitter generates an even parity. When '1', the transmitter generates an odd parity. Only applicable in standard UART and SmartCard submodes. Default Value: 0
2 : 0	STOP_BITS	Stop bits. STOP_BITS + 1 is the duration of the stop period in terms of halve bit periods. Valid range is [1, 7]; i.e. a stop period should last at least one bit period. Default Value: 2

9.1.9 SCB0_UART_RX_CTRL

UART receiver control

Address: 0x40240048

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None	RW	RW	RW	None	RW		
HW Access	None	R	R	R	None	R		
Name	None	POLARITY	PARITY_ENABLED	PARITY	None	STOP_BITS [2:0]		

Bits	15	14	13	12	11	10	9	8
SW Access	None		RW	RW	None	RW	RW	RW
HW Access	None		R	R	None	R	R	R
Name	None [15:14]		SKIP_START	LIN_MODE	None	MP_MODE	DROP_ON_FRAME_ERROR	DROP_ON_PARITY_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None				RW			
HW Access	None				R			
Name	None [23:20]				BREAK_WIDTH [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None							RW
HW Access	None							R
Name	None [31:25]							BREAK_LEVEL

Bits	Name	Description
24	BREAK_LEVEL	0: low level pulse detection, like Break field in LIN protocol 1: high level pulse detection, like IFS field in CXPI protocol, or idle line state in UART Default Value: 0
19 : 16	BREAK_WIDTH	Break width. BREAK_WIDTH + 1 is the minimum width in bit periods of a break. During a break the transmitted/received line value is '0'. This feature is useful for standard UART submode and LIN submode ("break field" detection). Once, the break is detected, the INTR_RX.BREAK_DETECT bit is set to '1'. Note that break detection precedes baud rate detection, which is used to synchronize/refine the receiver clock to the transmitter clock. As a result, break detection operates with an unsynchronized/unrefined receiver clock. Therefore, the receiver's definition of a bit period is imprecise and the setting of this field should take this imprecision into account. The LIN standard also accounts for this imprecision: a LIN start bit followed by 8 data bits allows for up to 9 consecutive '0' bit periods during regular transmission, whereas the LIN break detection should be at least 13 consecutive '0' bit periods. This provides for a margin of 4 bit periods. Therefore, the default value of this field is set to 10, representing a minimal break field with of 10+1 = 11 bit periods; a value in between the 9 consecutive bit periods of a regular transmission and the 13 consecutive bit periods of a break field. This provides for slight imprecisions of the receiver clock wrt. the transmitter clock. There should not be a need to program this field to any value other than its default value. Default Value: 10

9.1.9 SCB0_UART_RX_CTRL (continued)

13	SKIP_START	Only applicable in standard UART submode. When '1', the receiver skips start bit detection for the first received data frame. Instead, it synchronizes on the first received data frame bit, which should be a '1'. This functionality is intended for wake up from DeepSleep when receiving a data frame. The transition from idle ('1') to START ('0') on the RX line is used to wake up the CPU. The transition detection (and the associated wake up functionality) is performed by the GPIO2 IP. The woken up CPU will enable the SCB's UART receiver functionality. Once enabled, it is assumed that the START bit is ongoing (the CPU wakeup and SCB enable time should be less than the START bit period). The SCB will synchronize to a '0' to '1' transition, which indicates the first data frame bit is received (first data frame bit should be '1'). After synchronization to the first data frame bit, the SCB will resume normal UART functionality: subsequent data frames will be synchronized on the receipt of a START bit. Default Value: 0
12	LIN_MODE	Only applicable in standard UART submode. When '1', the receiver performs break detection and baud rate detection on the incoming data. First, break detection counts the amount of bit periods that have a line value of '0'. BREAK_WIDTH specifies the minimum required amount of bit periods. Successful break detection sets the INTR_RX.BREAK_DETECT interrupt cause to '1'. Second, baud rate detection counts the amount of peripheral clock periods that are used to receive the synchronization byte (0x55; least significant bit first). The count is available through UART_RX_STATUS.BR_COUNTER. Successful baud rate detection sets the INTR_RX.BAUD_DETECT interrupt cause to '1' (BR_COUNTER is reliable). This functionality is used to synchronize/refine the receiver clock to the transmitter clock. The receiver software can use the BR_COUNTER value to set the right IP clock (from the programmable clock IP) to guarantee successful receipt of the first LIN data frame (Protected Identifier Field) after the synchronization byte. Default Value: 0
10	MP_MODE	Multi-processor mode. When '1', multi-processor mode is enabled. In this mode, RX_CTRL.DATA_WIDTH should indicate a 9-bit data frame. In multi-processor mode, the 9th received bit of a data frame separates addresses (bit is '1') from data (bit is '0'). A received address is matched with RX_MATCH.DATA and RX_MATCH.MASK. In the case of a match, subsequent received data are sent to the RX FIFO. In the case of NO match, subsequent received data are dropped. Default Value: 0
9	DROP_ON_FRAME_ERROR	Behavior when an error is detected in a start or stop period. When '0', received data is sent to the RX FIFO. When '1', received data is dropped and lost. Default Value: 0
8	DROP_ON_PARITY_ERROR	Behavior when a parity check fails. When '0', received data is sent to the RX FIFO. When '1', received data is dropped and lost. Only applicable in standard UART and SmartCard submodes (negatively acknowledged SmartCard data frames may be dropped with this field). Default Value: 0
6	POLARITY	Inverts incoming RX line signal. Inversion is after local loopback. This functionality is intended for IrDA receiver functionality. Default Value: 0
5	PARITY_ENABLED	Parity checking enabled ('1') or not ('0'). Only applicable in standard UART submode. In SmartCard submode, parity checking is always enabled through hardware. In IrDA submode, parity checking is always disabled through hardware. Default Value: 0
4	PARITY	Parity bit. When '0', the receiver expects an even parity. When '1', the receiver expects an odd parity. Only applicable in standard UART and SmartCard submodes. Default Value: 0
2 : 0	STOP_BITS	Stop bits. STOP_BITS + 1 is the duration of the stop period in terms of half bit periods. Valid range is [1, 7]; i.e. a stop period should last at least one bit period. Note that in case of a stop bits error, the successive data frames may get lost as the receiver needs to resynchronize its start bit detection. The amount of lost data frames depends on both the amount of stop bits, the idle time between data frames and the data frame value. Default Value: 2

9.1.10 SCB0_UART_RX_STATUS

UART receiver status

Address: 0x4024004C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	W							
Name	BR_COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None				R			
HW Access	None				W			
Name	None [15:12]				BR_COUNTER [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11 : 0	BR_COUNTER	Amount of SCB clock periods that constitute the transmission of a 0x55 data frame (sent least significant bit first) as determined by the receiver. BR_COUNTER / 8 is the amount of SCB clock periods that constitute a bit period. This field has valid data when INTR_RX.BAUD_DETECT is set to '1'. Default Value: Undefined

9.1.11 SCB0_UART_FLOW_CTRL

UART flow control

Address: 0x40240050

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				TRIGGER_LEVEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							RTS_POLARITY

Bits	31	30	29	28	27	26	25	24
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [31:26]						CTS_ENABLED	CTS_POLARITY

Bits	Name	Description
25	CTS_ENABLED	Enable use of CTS input signal by the UART transmitter: '0': Disabled. The UART transmitter ignores the CTS input signal and transmits when a data frame is available for transmission in the TX FIFO or the TX shift register. '1': Enabled. The UART transmitter uses CTS input signal to qualify the transmission of data. It transmits when CTS input signal is active and a data frame is available for transmission in the TX FIFO or the TX shift register. If UART_CTRL.LOOPBACK is '1', the CTS input signal is driven by the RTS output signal locally in SCB (both signals are subjected to signal polarity changes are indicated by RTS_POLARITY and CTS_POLARITY). Default Value: 0
24	CTS_POLARITY	Polarity of the CTS input signal '0': CTS is active low ; '1': CTS is active high; Default Value: 0
16	RTS_POLARITY	Polarity of the RTS output signal: '0': RTS is active low; '1': RTS is active high; During SCB reset (Hibernate system power mode), RTS output signal is '1'. This represents an inactive state assuming an active low polarity. Default Value: 0

9.1.11 SCB0_UART_FLOW_CTRL (continued)

3 : 0	TRIGGER_LEVEL	Trigger level. When the receiver FIFO has less entries than the amount of this field, a Ready To Send (RTS) output signal is activated. By setting this field to "0", flow control is effectively disabled (may be useful for debug purposes). Default Value: 0
-------	---------------	--

9.1.12 SCB0_I2C_CTRL

I2C control

Address: 0x40240060

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW				RW			
HW Access	R				R			
Name	LOW_PHASE_OVS [7:4]				HIGH_PHASE_OVS [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	RW	RW	RW	RW	RW	None	RW	RW
HW Access	R	R	R	R	R	None	R	R
Name	S_NOT_READY_- DATA_NACK	S_NOT_READY_AD- DR_NACK	S_READY_DATA_ACK	S_READY_ADDR_ACK	S_GENERAL_IGNORE	None	M_NOT_READY_- DATA_NACK	M_READY_DATA_ACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							LOOPBACK

Bits	31	30	29	28	27	26	25	24
SW Access	RW	RW	None					
HW Access	R	R	None					
Name	MASTER_MODE	SLAVE_MODE	None [29:24]					

Bits	Name	Description
31	MASTER_MODE	Master mode enabled ('1') or not ('0'). Note that both master and slave modes can be enabled at the same time. This allows the IP to address itself. Default Value: 0
30	SLAVE_MODE	Slave mode enabled ('1') or not ('0'). Default Value: 0
16	LOOPBACK	Local loopback control (does NOT affect the information on the pins). Only applicable in master/slave mode. When '0', no loopback When '1', loopback is enabled internally in the peripheral, and as a result unaffected by other I2C devices. This allows a SCB I2C peripheral to address itself. Default Value: 0
15	S_NOT_READY_- DATA_NACK	Only used when: - non EZ mode Functionality is as follows: - 1: a received data element byte the slave is immediately NACK'd when the receiver FIFO is full. - 0: clock stretching is performed (till the receiver FIFO is no longer full). Default Value: 1

9.1.12 SCB0_I2C_CTRL (continued)

14	S_NOT_READY_ADDR_NACK	This field is used during an address match or general call address in internally clocked mode Only used when: - EC_AM_MODE is '0', EC_OP_MODE is '0', S_GENERAL_IGNORE is '0' and non EZ mode. Functionality is as follows: - 1: a received (matching) slave address is immediately NACK'd when the receiver FIFO is full. - 0: clock stretching is performed (till the receiver FIFO is no longer full). For externally clocked logic (EC_AM is '1') on an address match or general call address (and S_GENERAL_IGNORE is '0'). Only used when (NOT used when EC_AM is '1' and EC_OP is '1' and address match and EZ mode): - EC_AM is '1' and EC_OP is '0'. - EC_AM is '1' and general call address match. - EC_AM is '1' and non EZ mode. Functionality is as follows: - 1: a received (matching or general) slave address is always immediately NACK'd. There are two possibilities: 1). the SCB clock is available (in Active system power mode) and it handles the rest of the current transfer. In this case the I2C master will not observe the NACK. 2). SCB clock is not present (in DeepSleep system power mode). In this case the I2C master will observe the NACK and may retry the transfer in the future (which gives the internally clocked logic the time to wake up from DeepSleep system power mode). - 0: clock stretching is performed (till the SCB clock is available). The logic will handle the ongoing transfer as soon as the clock is enabled. Default Value: 1
13	S_READY_DATA_ACK	When '1', a received data element by the slave is immediately ACK'd when the receiver FIFO is not full. In EZ mode, this field should be set to '1'. Default Value: 1
12	S_READY_ADDR_ACK	When '1', a received (matching) slave address is immediately ACK'd when the receiver FIFO is not full. In EZ mode, this field should be set to '1'. Default Value: 1
11	S_GENERAL_IGNORE	When '1', a received general call slave address is immediately NACK'd (no ACK or clock stretching) and treated as a non matching slave address. This is useful for slaves that do not need any data supplied within the general call structure. Default Value: 1
9	M_NOT_READY_DATA_NACK	for I2C master, the NACKed byte should be properly received. it write the data byte, before ACK/NACK decision. When '1', if a received data element byte is written, and the receiver FIFO become full, the master send out NACK . if the receiver FIFO is full (the received data byte cannot be written), it stretch SCL(extend SCL low phase) until the receiver FIFO changes to not full, to write the last byte, then send out NACK. When '0', clock stretching is used instead (till the receiver FIFO is no longer full). Default Value: 1
8	M_READY_DATA_ACK	When '1', a received data element by the master is immediately ACK'd when the receiver FIFO is not full. Default Value: 1
7 : 4	LOW_PHASE_OVS	Serial I2C interface low phase oversampling factor. LOW_PHASE_OVS + 1 SCB clock periods constitute the low phase of a bit period. The valid range is [7, 15] with input signal median filtering and [6, 15] without input signal median filtering. The field is only used in master mode. In slave mode, the field is NOT used. However, there is a frequency requirement for the SCB clock wrt. the regular (no stretching) interface (IF) low time to guarantee functionally correct behavior. With input signal median filtering, the IF low time should be ≥ 8 SCB clock cycles and ≤ 16 IP clock cycles. Without input signal median filtering, the IF low time should be ≥ 7 SCB clock cycles and ≤ 16 SCB clock cycles. in slave mode, this field is used to define number of clk_scb cycles for tSU-DAT timing (from ACK/NACK/data ready, to SCL rising edge (released from I2C slave clock stretching)) Default Value: 8

9.1.12 SCB0_I2C_CTRL (continued)

3 : 0	HIGH_PHASE_OVS	Serial I2C interface high phase oversampling factor. HIGH_PHASE_OVS + 1 SCB clock periods constitute the high phase of a bit period. The valid range is [5, 15] with input signal median filtering and [4, 15] without input signal median filtering. The field is only used in master mode. In slave mode, the field is NOT used. However, there is a frequency requirement for the SCB clock wrt. the regular interface (IF) high time to guarantee functional correct behavior. With input signal median filtering, the IF high time should be ≥ 6 SCB clock cycles and ≤ 16 SCB clock cycles. Without input signal median filtering, the IF high time should be ≥ 5 SCB clock cycles and ≤ 16 SCB clock cycles. Default Value: 8
-------	----------------	---

9.1.13 SCB0_I2C_STATUS

I2C status

Address: 0x40240064

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		R	R	None	R	R	R
HW Access	None		W	W	None	W	W	W
Name	None [7:6]		M_READ	S_READ	None	I2CS_IC_B USY	I2C_EC_BU SY	BUS_BUSY

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	W							
Name	CURR_EZ_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	W							
Name	BASE_EZ_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 16	BASE_EZ_ADDR	I2C slave base EZ address. Address as provided by an I2C write transfer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable, as clock domain synchronization is not performed in the design. Default Value: Undefined
15 : 8	CURR_EZ_ADDR	I2C slave current EZ address. Current address pointer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable (during an ongoing transfer when I2C_EC_BUSY is '1'), as clock domain synchronization is not performed in the design. Default Value: Undefined
5	M_READ	I2C master read transfer ('1') or I2C master write transfer ('0'). When the I2C master is inactive/ idle or transmitting START, REPEATED START, STOP or an address, this field is '0'. Default Value: 0
4	S_READ	I2C slave read transfer ('1') or I2C slave write transfer ('0'). When the I2C slave is inactive/idle or receiving START, REPEATED START, STOP or an address, this field is '0'. Default Value: 0
2	I2CS_IC_BUSY	Indicates whether the internally clocked slave logic is being accessed by external I2C master. --set at ADDR_MATCH --clear at START/RESET, STOP detection, or BUS_ERROR This bit can be used by SW to determine whether I2CS_IC is busy before entering DeepSleep. Default Value: 0
1	I2C_EC_BUSY	Indicates whether the externally clocked logic is potentially accessing the EZ memory and/or updating BASE_EZ_ADDR or CURR_EZ_ADDR (this is only possible in EZ mode). This bit can be used by SW to determine whether BASE_EZ_ADDR and CURR_EZ_ADDR are reliable. Default Value: Undefined

9.1.13 SCB0_I2C_STATUS (continued)

0	BUS_BUSY	I2C bus is busy. The bus is considered busy ('1'), from the time a START is detected or from the time the SCL line is '0'. The bus is considered idle ('0'), from the time a STOP is detected. If SCB block is disabled, BUS_BUSY is '0'. After enabling the block, it takes time for the BUS_BUSY to detect a busy bus. This time is the maximum high time of the SCL line. For a 100 kHz interface frequency, this maximum high time may last roughly 5 us (half a bit period). For single master systems, BUS_BUSY does not have to be used to detect an idle bus before a master starts a transfer using I2C_M_CMD.M_START (no bus collisions). For multi-master systems, BUS_BUSY can be used to detect an idle bus before a master starts a transfer using I2C_M_CMD.M_START_ON_IDLE (to prevent bus collisions). Default Value: 0
---	----------	--

9.1.14 SCB0_I2C_M_CMD

I2C master command

Address: 0x40240068

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	RW	RW	RW	RW
HW Access	None			RW1C	RW1C	RW1C	RW1C	RW1C
Name	None [7:5]			M_STOP	M_NACK	M_ACK	M_START_ON_IDLE	M_START

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
4	M_STOP	When '1', attempt to transmit a STOP. When this action is performed, the hardware sets this field to '0'. I2C_M_CMD.M_START has a higher priority than this command: in situations where both a STOP and a REPEATED START could be transmitted, M_START takes precedence over M_STOP. Default Value: 0
3	M_NACK	for I2C master, the NACKed byte should be properly received. it write the data byte, before ACK/ NACK decision. When '1', attempt to transmit a negative acknowledgement (NACK). if the reciever FIFO is full (the received data byte cannot be written), it stretch SCL(extend SCL low phase) until the receiver FIFO changes to not full, to write the last byte, then send out NACK. When this action is performed, the hardware sets this field to '0'. Default Value: 0
2	M_ACK	When '1', attempt to transmit an acknowledgement (ACK). When this action is performed, the hardware sets this field to '0'. Default Value: 0
1	M_START_ON_IDLE	When '1', transmit a START as soon as the bus is idle (I2C_STATUS.BUS_BUSY is '0', note that BUSY has a default value of '0'). For bus idle detection the hardware relies on STOP detection. As a result, bus idle detection is only functional after at least one I2C bus transfer has been detected on the bus (default/reset value of BUSY is '0') . A START is only transmitted when the master state machine is in the default state. When this action is performed, the hardware sets this field to '0'. Default Value: 0

9.1.14 SCB0_I2C_M_CMD (continued)

0	M_START	When '1', transmit a START or REPEATED START. Whether a START or REPEATED START is transmitted depends on the state of the master state machine. A START is only transmitted when the master state machine is in the default state. A REPEATED START is transmitted when the master state machine is not in the default state, but is working on an ongoing transaction. The REPEATED START can only be transmitted after a NACK or ACK has been received for a transmitted data element or after a NACK has been transmitted for a received data element. When this action is performed, the hardware sets this field to '0'. Default Value: 0
---	---------	--

9.1.15 SCB0_I2C_S_CMD

I2C slave command

Address: 0x4024006C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW	RW	RW
HW Access	None					R	RW1C	RW1C
Name	None [7:3]					S_TX- _ONES_ON _EMPTY	S_NACK	S_ACK

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
2	S_TX_ONES_ON_EMPTY	When '1', attempt to send ones when TX_FIFO is empty. Once hardware starts to send ones, it will continue send ones until NACK is received, regardless of TX_FIFO status (even if new data is written into TX_FIFO). This bit is used to avoid stretching SCL, which is not expected for some master devices. Default Value: 0
1	S_NACK	When '1', attempt to transmit a negative acknowledgement (NACK). When this action is performed, the hardware sets this field to '0'. In EZ mode, this field should be set to '0' (it is only to be used in non EZ mode). This command has a higher priority than I2C_S_CMD.S_ACK, I2C_CTRL.S_READY_ADDR_ACK or I2C_CTRL.S_READY_DATA_ACK. Default Value: 0
0	S_ACK	When '1', attempt to transmit an acknowledgement (ACK). When this action is performed, the hardware sets this field to '0'. In EZ mode, this field should be set to '0' (it is only to be used in non EZ mode). Default Value: 0

9.1.16 SCB0_I2C_CFG

I2C configuration

Address: 0x40240070

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	None		RW	
HW Access	None			R	None		R	
Name	None [7:5]			SDA_IN_FILT_SEL	None [3:2]		SDA_IN_FILT_TRIM [1:0]	

Bits	15	14	13	12	11	10	9	8
SW Access	None			RW	None		RW	
HW Access	None			R	None		R	
Name	None [15:13]			SCL_IN_FILT_SEL	None [11:10]		SCL_IN_FILT_TRIM [9:8]	

Bits	23	22	21	20	19	18	17	16
SW Access	None		RW		RW		RW	
HW Access	None		R		R		R	
Name	None [23:22]		SDA_OUT_FILT2_TRIM [21:20]		SDA_OUT_FILT1_TRIM [19:18]		SDA_OUT_FILT0_TRIM [17:16]	

Bits	31	30	29	28	27	26	25	24
SW Access	None		RW		None			
HW Access	None		R		None			
Name	None [31:30]		SDA_OUT_FILT_SEL [29:28]		None [27:24]			

Bits	Name	Description
29 : 28	SDA_OUT_FILT_SEL	Selection of cumulative filter delay on SDA output to meet tHD_DAT parameter "0": 0 ns. "1": 50 ns (filter 0 enabled). "2": 100 ns (filters 0 and 1 enabled). "3": 150 ns (filters 0, 1 and 2 enabled). Default Value: 0
21 : 20	SDA_OUT_FILT2_TRIM	Trim settings for the 50ns delay filter on SDA output used to guarantee tHD_DAT I2C parameter. Default setting meets the I2C spec. Programmability available if required Default Value: 2
19 : 18	SDA_OUT_FILT1_TRIM	Trim settings for the 50ns delay filter on SDA output used to guarantee tHD_DAT I2C parameter. Default setting meets the I2C spec. Programmability available if required Default Value: 2
17 : 16	SDA_OUT_FILT0_TRIM	Trim settings for the 50ns delay filter on SDA output used to guarantee tHD_DAT I2C parameter. Default setting meets the I2C spec. Programmability available if required Default Value: 2
12	SCL_IN_FILT_SEL	Enable for 50ns glitch filter on SCL input '0': 0 ns. '1': 50 ns (filter enabled). Default Value: 1

9.1.16 SCB0_I2C_CFG (continued)

9 : 8	SCL_IN_FILT_TRIM	Trim settings for the 50ns glitch filter on the SDA input. Default setting meets the I2C glitch rejections specs. Programmability available if required Default Value: 0
4	SDA_IN_FILT_SEL	Enable for 50ns glitch filter on SDA input '0': 0 ns. '1': 50 ns (filter enabled). Default Value: 1
1 : 0	SDA_IN_FILT_TRIM	Trim settings for the 50ns glitch filter on the SDA input. Default setting meets the I2C glitch rejections specs. Programmability available if required Default Value: 3

9.1.17 SCB0_I2C_STRETCH_CTRL

I2C stretch control

Address: 0x40240074

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				STRETCH_THRESHOLD [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3 : 0	STRETCH_THRESHOLD	stretch threshold. Typically it is the SCL turaround delay (including IO cell delay, SCL rise time, analog filter delay), in number of clk_scb cycles. When STRETCH_COUNT is higher than this STRETCH_THRESHOLD, STRETCH_DETECTED will be set. STRETCH_DETECTED should be less than "HOVS-2", HOVS means I2C_CTRL.HIGH_PHASE_OVS, or I2C_CTRL_HS.HOVS_HS. Default Value: 0

9.1.18 SCB0_I2C_STRETCH_STATUS

I2C stretch status

Address: 0x40240078

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		R	R	R			
HW Access	None		W	W	W			
Name	None [7:6]		SYNC_DETECTED	STRETCH_DETECTED	STRETCH_COUNT [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							STRETCHING

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	STRETCHING	I2C SCL is stretched by this block (DUT), for I2C master, this can happen when TX FIFO is empty, or RX_FIFO is full, or ACK/NACK is not decided, or RESTART/STOP is not decided. For I2C slave, this can heppend, TX FIFO is empty, or RX_FIFO is full, or ACK/NACK is not decided. Default Value: 0
5	SYNC_DETECTED	synchronization detected. Set when I2C falling edge comes in earlier than expected (suppressed by another I2C master during synchronization). Default Value: 0
4	STRETCH_DETECTED	stretch detected. Set when I2C rising edge comes later than expected (suppressed by another master or slave), and STRETCH_COUNT is higher than STRETCH_THRESHOLD. Default Value: 0
3 : 0	STRETCH_COUNT	stretch count. Started when I2C device start to drive high phase on internal SCL output signal, stalled when it detected high level on SCL input signal. Default Value: 0

9.1.19 SCB0_TX_CTRL

Transmitter control

Address: 0x40240200

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW				
HW Access	None			R				
Name	None [7:5]			DATA_WIDTH [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							MSB_- FIRST

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [23:18]						OPEN_DRA IN_SCL	OPEN_DRA IN

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
17	OPEN_DRAIN_SCL	Each IO cell "xxx" has two associated IP output signals "xxx_out_en" and "xxx_out". '0': Normal operation mode. Typically, this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by a single IO cell. In this operation mode, for an IO cell "xxx" that is used as an output, the "xxx_out_en" output enable signal is typically constant '1' the "xxx_out" output is the outputted value. In other words, in normal operation mode, the "xxx_out" output is used to control the IO cell output value: "xxx_out" is '0' to drive an IO cell output value of '0' and "xxx_out" is '1' to drive an IO cell output value of '1'. '1': Open drain operation mode. Typically this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by multiple IO cells (possibly on multiple chips). In this operation mode, for an IO cell "xxx" that is used as an output, the "xxx_out_en" output controls the outputted value. Typically, open drain operation mode drives low/'0' and the "xxx_out" output is constant '1'. In other words, in open drain operation mode, the "xxx_out_en" output is used to control the IO cell output value: in drive low/'0' mode: "xxx_out_en" is '1' (drive enabled) to drive an IO cell output value of '0' and "xxx_out_en" is '1' (drive disabled) to not drive an IO cell output value (another IO cell can drive the wire/line or a pull up results in a wire/line value '1'). this bit is applicable to I2C SCL only. I2C SDA always work in open-drain mode. this is not applicable to M0S8, which does not need special control in SCB for open-drain drive mode. Default Value: 1

9.1.19 SCB0_TX_CTRL (continued)

16	OPEN_DRAIN	Each IO cell "xxx" has two associated IP output signals "xxx_out_en" and "xxx_out". '0': Normal operation mode. Typically, this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by a single IO cell. In this operation mode, for an IO cell "xxx" that is used as an output, the "xxx_out_en" output enable signal is typically constant '1' the "xxx_out" output is the outputted value. In other words, in normal operation mode, the "xxx_out" output is used to control the IO cell output value: "xxx_out" is '0' to drive an IO cell output value of '0' and "xxx_out" is '1' to drive an IO cell output value of '1'. '1': Open drain operation mode. Typically this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by multiple IO cells (possibly on multiple chips). In this operation mode, for an IO cell "xxx" that is used as an output, the "xxx_out_en" output controls the outputted value. Typically, open drain operation mode drives low/'0' and the "xxx_out" output is constant '1'. In other words, in open drain operation mode, the "xxx_out_en" output is used to control the IO cell output value: in drive low/'0' mode: "xxx_out_en" is '1' (drive enabled) to drive an IO cell output value of '0' and "xxx_out_en" is '1' (drive disabled) to not drive an IO cell output value (another IO cell can drive the wire/line or a pull up results in a wire/line value '1'). The open drain mode is supported for: - UART mode, "uart_tx" IO cell. - SPI mode, "spi_miso" IO cell. this bit is not applicable to I2C mode, "i2c_scl" and "i2c_sda" IO cells. Default Value: 0
8	MSB_FIRST	Least significant bit first ('0') or most significant bit first ('1'). For I2C, this field should be '1'. Default Value: 1
4 : 0	DATA_WIDTH	Dataframe width, depending on CTRL.MEM_WIDTH. DATA_WIDTH + 1 is the amount of bits in a transmitted data frame. This number does not include start, parity and stop bits. For UART mode, the valid range is [3, 8]. For SPI, the valid range is [3, 31]. For I2C the only valid value is 7. In EZ mode (for both SPI and I2C), the only valid value is 7. Default Value: 7

9.1.20 SCB0_TX_FIFO_CTRL

Transmitter FIFO control

Address: 0x40240204

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				TRIGGER_LEVEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [23:18]						FREEZE	CLEAR

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
17	FREEZE	When '1', hardware reads from the transmitter FIFO do not remove FIFO entries. Freeze will not advance the TX FIFO read pointer. Default Value: 0
16	CLEAR	When '1', the transmitter FIFO and transmitter shift register are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period. Default Value: 0
3 : 0	TRIGGER_LEVEL	Trigger level. When the transmitter FIFO has less entries than the number of this field, a transmitter trigger event INTR_TX.TRIGGER is generated. Default Value: 0

9.1.21 SCB0_TX_FIFO_STATUS

Transmitter FIFO status

Address: 0x40240208

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R				
HW Access	None			W				
Name	None [7:5]			USED [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	R	None						
HW Access	W	None						
Name	SR_VALID	None [14:8]						

Bits	23	22	21	20	19	18	17	16
SW Access	None				R			
HW Access	None				W			
Name	None [23:20]				RD_PTR [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None				R			
HW Access	None				W			
Name	None [31:28]				WR_PTR [27:24]			

Bits	Name	Description
27 : 24	WR_PTR	FIFO write pointer: FIFO location at which a new data frame is written. Default Value: 0
19 : 16	RD_PTR	FIFO read pointer: FIFO location from which a data frame is read by the hardware. Default Value: 0
15	SR_VALID	Indicates whether the TX shift registers holds a valid data frame ('1') or not ('0'). The shift register can be considered the top of the TX FIFO (the data frame is not included in the USED field of the TX FIFO). The shift register is a working register and holds the data frame that is currently transmitted (when the protocol state machine is transmitting a data frame) or the data frame that is transmitted next (when the protocol state machine is not transmitting a data frame). Default Value: 0
4 : 0	USED	Amount of entries in the transmitter FIFO. The value of this field ranges from 0 to FF_DATA_NR (EZ_DATA_NR/2). Default Value: 0

9.1.22 SCB0_TX_FIFO_WR

Transmitter FIFO write

Address: 0x40240240

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	W							
HW Access	R							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	W							
HW Access	R							
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	W							
HW Access	R							
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	W							
HW Access	R							
Name	DATA [31:24]							

Bits	Name	Description
31 : 0	DATA	Data frame written into the transmitter FIFO. Behavior is similar to that of a PUSH operation. Note that when CTRL.MEM_WIDTH is "0", only DATA[7:0] are used and when CTRL.MEM_WIDTH is "1", only DATA[15:0] are used. A write to a full TX FIFO sets INTR_TX.OVERFLOW to '1'. Default Value: 0

9.1.23 SCB0_RX_CTRL

Receiver control

Address: 0x40240300

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW				
HW Access	None			R				
Name	None [7:5]			DATA_WIDTH [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [15:10]						MEDIAN	MSB_ - FIRST

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	MEDIAN	Median filter. When '1', a digital 3 taps median filter is performed on input interface lines. This filter should reduce the susceptibility to errors. However, its requires higher oversampling values. For UART IrDA submode, this field should always be '1'. Default Value: 0
8	MSB_FIRST	Least significant bit first ('0') or most significant bit first ('1'). For I2C, this field should be '1'. Default Value: 1
4 : 0	DATA_WIDTH	Dataframe width, depending on CTRL.MEM_WIDTH. DATA_WIDTH + 1 is the expected amount of bits in received data frame. This number does not include start, parity and stop bits. For UART mode, the valid range is [3, 8]. For SPI, the valid range is [3, 31]. For I2C the only valid value is 7. In EZ mode (for both SPI and I2C), the only valid value is 7. Default Value: 7

9.1.24 SCB0_RX_FIFO_CTRL

Receiver FIFO control

Address: 0x40240304

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW			
HW Access	None				R			
Name	None [7:4]				TRIGGER_LEVEL [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [23:18]						FREEZE	CLEAR

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
17	FREEZE	When '1', hardware writes to the receiver FIFO have no effect. Freeze will not advance the RX FIFO write pointer. Default Value: 0
16	CLEAR	When '1', the receiver FIFO and receiver shift register are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period. Default Value: 0
3 : 0	TRIGGER_LEVEL	Trigger level. When the receiver FIFO has more entries than the number of this field, a receiver trigger event INTR_RX.TRIGGER is generated. Default Value: 0

9.1.25 SCB0_RX_FIFO_STATUS

Receiver FIFO status

Address: 0x40240308

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R				
HW Access	None			W				
Name	None [7:5]			USED [4:0]				

Bits	15	14	13	12	11	10	9	8
SW Access	R	None						
HW Access	W	None						
Name	SR_VALID	None [14:8]						

Bits	23	22	21	20	19	18	17	16
SW Access	None				R			
HW Access	None				W			
Name	None [23:20]				RD_PTR [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	None				R			
HW Access	None				W			
Name	None [31:28]				WR_PTR [27:24]			

Bits	Name	Description
27 : 24	WR_PTR	FIFO write pointer: FIFO location at which a new data frame is written by the hardware. Default Value: 0
19 : 16	RD_PTR	FIFO read pointer: FIFO location from which a data frame is read. Default Value: 0
15	SR_VALID	Indicates whether the RX shift registers holds a (partial) valid data frame ('1') or not ('0'). The shift register can be considered the bottom of the RX FIFO (the data frame is not included in the USED field of the RX FIFO). The shift register is a working register and holds the data frame that is currently being received (when the protocol state machine is receiving a data frame). Default Value: 0
4 : 0	USED	Amount of entries in the receiver FIFO. The value of this field ranges from 0 to FF_DATA_NR (EZ_DATA_NR/2). Default Value: 0

9.1.26 SCB0_RX_MATCH

Slave address and mask

Address: 0x40240310

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	MASK [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 16	MASK	Slave device address mask. This field is a mask that specifies which of the slave address bits take part in the matching. $MATCH = ((ADDR \& MASK) == ("slave\ address" \& MASK))$. Default Value: 0
7 : 0	ADDR	Slave device address. In UART multi-processor mode, all 8 bits are used. In I2C slave mode, only bits 7 down to 1 are used. This reflects the organization of the first transmitted byte in a I2C transfer: the first 7 bits represent the address of the addressed slave, and the last 1 bit is a read/write indicator ('0': write, '1': read). Default Value: 0

9.1.27 SCB0_RX_FIFO_RD

Receiver FIFO read

Address: 0x40240340

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	W							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	W							
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	W							
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	W							
Name	DATA [31:24]							

Bits	Name	Description
31 : 0	DATA	Data read from the receiver FIFO. Reading a data frame will remove the data frame from the FIFO; i.e. behavior is similar to that of a POP operation. Note that when CTRL.MEM_WIDTH is "0", only DATA[7:0] are used and when CTRL.MEM_WIDTH is "1", only DATA[15:0] are used A read from an empty RX FIFO sets INTR_RX.UNDERFLOW to '1'. When this register is read through the debugger, the data frame will not be removed from the FIFO. Similar in operation to RX_FIFO_RD_SILENT Default Value: Undefined

9.1.28 SCB0_RX_FIFO_RD_SILENT

Receiver FIFO read silent

Address: 0x40240344

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	W							
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	W							
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	W							
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	W							
Name	DATA [31:24]							

Bits	Name	Description
31 : 0	DATA	Data read from the receiver FIFO. Reading a data frame will NOT remove the data frame from the FIFO; i.e. behavior is similar to that of a PEEK operation. Note that when CTRL.MEM_WIDTH is "0", only DATA[7:0] are used and when CTRL.MEM_WIDTH is "1", only DATA[15:0] are used A read from an empty RX FIFO sets INTR_RX.UNDERFLOW to '1'. Default Value: Undefined

9.1.29 SCB0_EZ_DATA0

Memory buffer

Address: 0x40240400

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	RW							
Name	EZ_DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	EZ_DATA	Data in buffer memory location. In case of a blocked discarded access, a read access returns 0xffff.ffff and a write access is dropped. Note that the 0xffff.ffff value is unique (not a legal EZ_DATA byte value) and can be detected by SW. Note that a discarded write access can be detected by reading back the written value. Default Value: Undefined

9.1.30 SCB0_INTR_CAUSE

Active clocked interrupt signal

Address: 0x40240E00

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None		R	R	R	R	R	R
HW Access	None		W	W	W	W	W	W
Name	None [7:6]		SPI_EC	I2C_EC	RX	TX	S	M

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
5	SPI_EC	Externally clocked SPI interrupt active ("interrupt_spi_ec"): INTR_SPI_EC_MASKED != 0. Default Value: 0
4	I2C_EC	Externally clock I2C interrupt active ("interrupt_i2c_ec"): INTR_I2C_EC_MASKED != 0. Default Value: 0
3	RX	Receiver interrupt active ("interrupt_rx"): INTR_RX_MASKED != 0. Default Value: 0
2	TX	Transmitter interrupt active ("interrupt_tx"): INTR_TX_MASKED != 0. Default Value: 0
1	S	Slave interrupt active ("interrupt_slave"): INTR_S_MASKED != 0. Default Value: 0
0	M	Master interrupt active ("interrupt_master"): INTR_M_MASKED != 0. Default Value: 0

9.1.31 SCB0_INTR_I2C_EC

Externally clocked I2C interrupt request

Address: 0x40240E80

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW1C	RW1C	RW1C	RW1C
HW Access	None				A	A	A	A
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	STOP detection after a read transfer occurred. Activated on the end of a read transfer (I2C STOP). This event is an indication that a buffer memory location has been read from. Only available for a slave request with an address match, in EZ and CMD_RESP modes, when CTRL.EC_OP_MODE is '1'. Default Value: 0
2	EZ_WRITE_STOP	STOP detection after a write transfer occurred. Activated on the end of a write transfer (I2C STOP). This event is an indication that a buffer memory location has been written to. For EZ mode: a transfer that only writes the base address does NOT activate this event. Only available for a slave request with an address match, in EZ and CMD_RESP modes, when CTRL.EC_OP_MODE is '1'. Default Value: 0
1	EZ_STOP	STOP detection. Activated on the end of a every transfer (I2C STOP). Only available for a slave request with an address match, in EZ and CMD_RESP modes, when CTRL.EC_OP_MODE is '1'. Default Value: 0
0	WAKE_UP	Wake up request. Active on incoming slave request (with address match). Only used when CTRL.EC_AM_MODE is '1'. Default Value: 0

9.1.32 SCB0_INTR_I2C_EC_MASK

Externally clocked I2C interrupt mask

Address: 0x40240E88

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	EZ_WRITE_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	EZ_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	WAKE_UP	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.33 SCB0_INTR_I2C_EC_MASKED

Externally clocked I2C interrupt masked

Address: 0x40240E8C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	Logical and of corresponding request and mask bits. Default Value: 0
2	EZ_WRITE_STOP	Logical and of corresponding request and mask bits. Default Value: 0
1	EZ_STOP	Logical and of corresponding request and mask bits. Default Value: 0
0	WAKE_UP	Logical and of corresponding request and mask bits. Default Value: 0

9.1.34 SCB0_INTR_SPI_EC

Externally clocked SPI interrupt request

Address: 0x40240EC0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW1C	RW1C	RW1C	RW1C
HW Access	None				A	A	A	A
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	STOP detection after a read transfer occurred. Activated on the end of a read transfer (SPI deselection). This event is an indication that a buffer memory location has been read from. Only used in EZ and CMD_RESP modes and when CTRL.EC_OP_MODE is '1'. Default Value: 0
2	EZ_WRITE_STOP	STOP detection after a write transfer occurred. Activated on the end of a write transfer (SPI deselection). This event is an indication that a buffer memory location has been written to. For EZ mode: a transfer that only writes the base address does NOT activate this event. Only used in EZ and CMD_RESP modes and when CTRL.EC_OP_MODE is '1'. Default Value: 0
1	EZ_STOP	STOP detection. Activated on the end of a every transfer (SPI deselection). Only available in EZ and CMD_RESP mode and when CTRL.EC_OP_MODE is '1'. Default Value: 0
0	WAKE_UP	Wake up request. Active on incoming slave request when externally clocked selection is '1'. Only used when CTRL.EC_AM_MODE is '1'. Default Value: 0

9.1.35 SCB0_INTR_SPI_EC_MASK

Externally clocked SPI interrupt mask

Address: 0x40240EC8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	EZ_WRITE_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	EZ_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	WAKE_UP	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.36 SCB0_INTR_SPI_EC_MASKED

Externally clocked SPI interrupt masked

Address: 0x40240ECC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [7:4]				EZ_READ_STOP	EZ_WRITE_STOP	EZ_STOP	WAKE_UP

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
3	EZ_READ_STOP	Logical and of corresponding request and mask bits. Default Value: 0
2	EZ_WRITE_STOP	Logical and of corresponding request and mask bits. Default Value: 0
1	EZ_STOP	Logical and of corresponding request and mask bits. Default Value: 0
0	WAKE_UP	Logical and of corresponding request and mask bits. Default Value: 0

9.1.37 SCB0_INTR_M

Master interrupt request

Address: 0x40240F00

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW1C	None	RW1C	RW1C	RW1C
HW Access	None			RW1S	None	RW1S	RW1S	RW1S
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW1C	RW1C
HW Access	None						RW1S	RW1S
Name	None [15:10]						SPI_DONE	I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	SPI_DONE	SPI master transfer done event: all data frames in the transmit FIFO are sent, the transmit FIFO is empty (both TX FIFO and transmit shifter register are empty), and SPI select output pin is de-selected. Default Value: 0
8	I2C_BUS_ERROR	I2C master bus error (unexpected detection of START or STOP condition). Default Value: 0
4	I2C_STOP	I2C master STOP. Set to '1', when the master has transmitted a STOP. Default Value: 0
2	I2C_ACK	I2C master acknowledgement. Set to '1', when the master receives a ACK (typically after the master transmitted the slave address or TX data). Default Value: 0
1	I2C_NACK	I2C master negative acknowledgement. Set to '1', when the master receives a NACK (typically after the master transmitted the slave address or TX data). Default Value: 0
0	I2C_ARB_LOST	I2C master lost arbitration: the value driven by the master on the SDA line is not the same as the value observed on the SDA line. The Firmware should clear the TX FIFO, to re-do this transfer. Default Value: 0

9.1.38 SCB0_INTR_M_SET

Master interrupt set request

Address: 0x40240F04

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW1S	None	RW1S	RW1S	RW1S
HW Access	None			A	None	A	A	A
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW1S	RW1S
HW Access	None						A	A
Name	None [15:10]						SPI_DONE	I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	SPI_DONE	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.39 SCB0_INTR_M_MASK

Master interrupt mask

Address: 0x40240F08

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	None	RW	RW	RW
HW Access	None			R	None	R	R	R
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None						RW	RW
HW Access	None						R	R
Name	None [15:10]						SPI_DONE	I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	SPI_DONE	Mask bit for corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.40 SCB0_INTR_M_MASKED

Master interrupt masked request

Address: 0x40240F0C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R	None	R	R	R
HW Access	None			W	None	W	W	W
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None						R	R
HW Access	None						W	W
Name	None [15:10]						SPI_DONE	I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	SPI_DONE	Logical and of corresponding request and mask bits. Default Value: 0
8	I2C_BUS_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
4	I2C_STOP	Logical and of corresponding request and mask bits. Default Value: 0
2	I2C_ACK	Logical and of corresponding request and mask bits. Default Value: 0
1	I2C_NACK	Logical and of corresponding request and mask bits. Default Value: 0
0	I2C_ARB_LOST	Logical and of corresponding request and mask bits. Default Value: 0

9.1.41 SCB0_INTR_S

Slave interrupt request

Address: 0x40240F40

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C
HW Access	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW1C	RW1C	RW1C	RW1C
HW Access	None				RW1S	RW1S	RW1S	RW1S
Name	None [15:12]				SPI_BUS_E RROR	SPI_EZ_ST OP	SPI_EZ_W RITE_STOP	I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW1C
HW Access	None							RW1S
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	I2C slave RESTART received. Set to '1', when REPEATED START event is detected. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') AND clock stretching is performed (I2C_CTRL.S_NOT_READY_ADDR_NACK is '0'), this field is NOT set. this is not applicable when address in previous transfer is master-code. Default Value: 0
11	SPI_BUS_ERROR	SPI slave deselected at an unexpected time in the SPI transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error. Default Value: 0
10	SPI_EZ_STOP	SPI slave deselected after any EZ SPI transfer occurred. Default Value: 0
9	SPI_EZ_WRITE_STOP	SPI slave deselected after a write EZ SPI transfer occurred. Default Value: 0
8	I2C_BUS_ERROR	I2C slave bus error (unexpected detection of START or STOP condition). This should not occur, it represents erroneous I2C bus behavior. In case of a bus error, the I2C slave state machine abort the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error. Default Value: 0

9.1.41 SCB0_INTR_S (continued)

7	I2C_GENERAL	I2C slave general call address received. If CTRL.ADDR_ACCEPT, the received address 0x00 (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected. Default Value: 0
6	I2C_ADDR_MATCH	I2C slave matching address received. If CTRL.ADDR_ACCEPT, the received address (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected. Default Value: 0
5	I2C_START	I2C slave START received. Set to '1', when START or REPEATED START event is detected. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') AND clock stretching is performed (I2C_CTRL.S_NOT_READY_ADDR_NACK is '0'), this field is NOT set. The Firmware should use INTR_S_EC.WAKE_UP, INTR_S_I2C_ADDR_MATCH and INTR_S_I2C_GENERAL. Default Value: 0
4	I2C_STOP	I2C STOP event for I2C (read or write) transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. The event is detected on any I2C transfer intended for this slave. Note that a I2C address intended for the slave (address is matching) will result in a I2C_STOP event independent of whether the I2C address is ACK'd or NACK'd. this is not applicable when address in previous transfer is master-code. Default Value: 0
3	I2C_WRITE_STOP	I2C STOP event for I2C write transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. In non EZ mode, the event is detected on any I2C write transfer intended for this slave. Note that a I2C write address intended for the slave (address is matching and a it is a write transfer) will result in a I2C_WRITE_STOP event independent of whether the I2C address is ACK'd or NACK'd. In EZ mode, the event is detected only on I2C write transfers that have EZ data written to the memory structure (an I2C write transfer that only communicates an I2C address and EZ address, will not result in this event being detected). this is not applicable when address in previous transfer is master-code. Default Value: 0
2	I2C_ACK	I2C slave acknowledgement received. Set to '1', when the slave receives a ACK (typically after the slave transmitted TX data). Default Value: 0
1	I2C_NACK	I2C slave negative acknowledgement received. Set to '1', when the slave receives a NACK (typically after the slave transmitted TX data). Default Value: 0
0	I2C_ARB_LOST	I2C slave lost arbitration: the value driven on the SDA line is not the same as the value observed on the SDA line (while the SCL line is '1'). This should not occur, it represents erroneous I2C bus behavior. In case of lost arbitration, the I2C slave state machine aborts the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error. Default Value: 0

9.1.42 SCB0_INTR_S_SET

Slave interrupt set request

Address: 0x40240F44

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
HW Access	A	A	A	A	A	A	A	A
Name	I2C_GENERAL	I2C_ADDR_MATCH	I2C_START	I2C_STOP	I2C_WRITE_STOP	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW1S	RW1S	RW1S	RW1S
HW Access	None				A	A	A	A
Name	None [15:12]				SPI_BUS_ERROR	SPI_EZ_STOP	SPI_EZ_WRITE_STOP	I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW1S
HW Access	None							A
Name	None [23:17]							I2C_RESTART

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
11	SPI_BUS_ERROR	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
10	SPI_EZ_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
9	SPI_EZ_WRITE_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
7	I2C_GENERAL	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
6	I2C_ADDR_MATCH	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
5	I2C_START	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
3	I2C_WRITE_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.42 SCB0_INTR_S_SET (continued)

2	I2C_ACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.43 SCB0_INTR_S_MASK

Slave interrupt mask

Address: 0x40240F48

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	RW	RW	RW	RW	RW
HW Access	R	R	R	R	R	R	R	R
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [15:12]				SPI_BUS_E RROR	SPI_EZ_ST OP	SPI_EZ_W RITE_STOP	I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Mask bit for corresponding bit in interrupt request register. Default Value: 0
11	SPI_BUS_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
10	SPI_EZ_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
9	SPI_EZ_WRITE_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
7	I2C_GENERAL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	I2C_ADDR_MATCH	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	I2C_START	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
3	I2C_WRITE_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.43 SCB0_INTR_S_MASK (continued)

2	I2C_ACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.44 SCB0_INTR_S_MASKED

Slave interrupt masked request

Address: 0x40240F4C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	R	R	R	R	R
HW Access	W	W	W	W	W	W	W	W
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [15:12]				SPI_BUS_E RROR	SPI_EZ_ST OP	SPI_EZ_W RITE_STOP	I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							R
HW Access	None							W
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Logical and of corresponding request and mask bits. Default Value: 0
11	SPI_BUS_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
10	SPI_EZ_STOP	Logical and of corresponding request and mask bits. Default Value: 0
9	SPI_EZ_WRITE_STOP	Logical and of corresponding request and mask bits. Default Value: 0
8	I2C_BUS_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
7	I2C_GENERAL	Logical and of corresponding request and mask bits. Default Value: 0
6	I2C_ADDR_MATCH	Logical and of corresponding request and mask bits. Default Value: 0
5	I2C_START	Logical and of corresponding request and mask bits. Default Value: 0
4	I2C_STOP	Logical and of corresponding request and mask bits. Default Value: 0
3	I2C_WRITE_STOP	Logical and of corresponding request and mask bits. Default Value: 0

9.1.44 SCB0_INTR_S_MASKED (continued)

2	I2C_ACK	Logical and of corresponding request and mask bits. Default Value: 0
1	I2C_NACK	Logical and of corresponding request and mask bits. Default Value: 0
0	I2C_ARB_LOST	Logical and of corresponding request and mask bits. Default Value: 0

9.1.45 SCB0_INTR_TX

Transmitter interrupt request

Address: 0x40240F80

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	RW1C	None		RW1C	RW1C
HW Access	RW1S	RW1S	RW1S	RW1S	None		RW1S	RW1S
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None					RW1C	RW1C	RW1C
HW Access	None					RW1S	RW1S	RW1S
Name	None [15:11]					UART_ARB_LOST	UART_DONE	UART_NACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
10	UART_ARB_LOST	UART lost arbitration: the value driven on the TX line is not the same as the value observed on the RX line. This condition event is useful when transmitter and receiver share a TX/RX line. This is the case in LIN or SmartCard modes. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
9	UART_DONE	UART transmitter done event. This happens when the IP is done transferring all data in the TX FIFO, and the last stop field is transmitted (both TX FIFO and transmit shifter register are empty). Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
8	UART_NACK	UART transmitter received a negative acknowledgement in SmartCard mode. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
7	BLOCKED	SW cannot get access to the EZ memory (EZ data access), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'. Default Value: 0
6	UNDERFLOW	Attempt to read from an empty TX FIFO. This happens when SCB is ready to transfer data and EMPTY is '1'. Only used in FIFO mode. Default Value: 0

9.1.45 SCB0_INTR_TX (continued)

5	OVERFLOW	Attempt to write to a full TX FIFO. Only used in FIFO mode. Default Value: 0
4	EMPTY	TX FIFO is empty; i.e. it has 0 entries. Only used in FIFO mode. Default Value: 0
1	NOT_FULL	TX FIFO is not full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is "0": # entries != FF_DATA_NR. MEM_WIDTH is "1": # entries != FF_DATA_NR/2. MEM_WIDTH is "2": # entries != FF_DATA_NR/4. Only used in FIFO mode. Default Value: 0
0	TRIGGER	Less entries in the TX FIFO than the value specified by TX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode. Default Value: 0

9.1.46 SCB0_INTR_TX_SET

Transmitter interrupt set request

Address: 0x40240F84

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	RW1S	None		RW1S	RW1S
HW Access	A	A	A	A	None		A	A
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None					RW1S	RW1S	RW1S
HW Access	None					A	A	A
Name	None [15:11]					UART_ARB_LOST	UART_DONE	UART_NACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
10	UART_ARB_LOST	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
9	UART_DONE	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
8	UART_NACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
7	BLOCKED	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	EMPTY	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	NOT_FULL	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.47 SCB0_INTR_TX_MASK

Transmitter interrupt mask

Address: 0x40240F88

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	RW	None		RW	RW
HW Access	R	R	R	R	None		R	R
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None					RW	RW	RW
HW Access	None					R	R	R
Name	None [15:11]					UART_ARB_LOST	UART_DONE	UART_NACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
10	UART_ARB_LOST	Mask bit for corresponding bit in interrupt request register. Default Value: 0
9	UART_DONE	Mask bit for corresponding bit in interrupt request register. Default Value: 0
8	UART_NACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
7	BLOCKED	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	EMPTY	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	NOT_FULL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.48 SCB0_INTR_TX_MASKED

Transmitter interrupt masked request

Address: 0x40240F8C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	R	None		R	R
HW Access	W	W	W	W	None		W	W
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None					R	R	R
HW Access	None					W	W	W
Name	None [15:11]					UART_ARB_LOST	UART_DONE	UART_NACK

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
10	UART_ARB_LOST	Logical and of corresponding request and mask bits. Default Value: 0
9	UART_DONE	Logical and of corresponding request and mask bits. Default Value: 0
8	UART_NACK	Logical and of corresponding request and mask bits. Default Value: 0
7	BLOCKED	Logical and of corresponding request and mask bits. Default Value: 0
6	UNDERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
5	OVERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
4	EMPTY	Logical and of corresponding request and mask bits. Default Value: 0
1	NOT_FULL	Logical and of corresponding request and mask bits. Default Value: 0
0	TRIGGER	Logical and of corresponding request and mask bits. Default Value: 0

9.1.49 SCB0_INTR_RX

Receiver interrupt request

Address: 0x40240FC0

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	None	RW1C	RW1C	None	RW1C
HW Access	RW1S	RW1S	RW1S	None	RW1S	RW1S	None	RW1S
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW1C	RW1C	RW1C	RW1C
HW Access	None				RW1S	RW1S	RW1S	RW1S
Name	None [15:12]				BREAK_DETECT	BAUD_DETECT	PARITY_ERROR	FRAME_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11	BREAK_DETECT	Break detection is successful: the line is '0' for UART_RX_CTRL.BREAK_WIDTH + 1 bit period. Can occur at any time to address unanticipated break fields; i.e. "break-in-data" is supported. This feature is supported for the UART standard and LIN submodes. For the UART standard submodes, ongoing receipt of data frames is NOT affected; i.e. Firmware is expected to take the proper action. For the LIN submode, possible ongoing receipt of a data frame is stopped and the (partially) received data frame is dropped and baud rate detection is started. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
10	BAUD_DETECT	LIN baudrate detection is completed. The receiver software uses the UART_RX_STATUS.BR_COUNTER value to set the right IP clock (from the programmable clock IP) to guarantee successful receipt of the first LIN data frame (Protected Identifier Field) after the synchronization byte. Set to '1', when event is detected. Write with '1' to clear bit. Default Value: 0
9	PARITY_ERROR	Parity error in received data frame. Set to '1', when event is detected. Write with '1' to clear bit. If UART_RX_CTL.DROP_ON_PARITY_ERROR is '1', the received frame is dropped. If UART_RX_CTL.DROP_ON_PARITY_ERROR is '0', the received frame is send to the RX FIFO. In SmartCard submode, negatively acknowledged data frames generate a parity error. Note that Firmware can only identify the erroneous data frame in the RX FIFO if it is fast enough to read the data frame before the hardware writes a next data frame into the RX FIFO. Default Value: 0

9.1.49 SCB0_INTR_RX (continued)

8	FRAME_ERROR	Frame error in received data frame. Set to '1', when event is detected. Write with '1' to clear bit. This can be either a start or stop bit(s) error: Start bit error: after the detection of the beginning of a start bit period (RX line changes from '1' to '0'), the middle of the start bit period is sampled erroneously (RX line is '1'). Note: a start bit error is detected BEFORE a data frame is received. Stop bit error: the RX line is sampled as '0', but a '1' was expected. Note: a stop bit error may result in failure to receive successive data frame(s). Note: a stop bit error is detected AFTER a data frame is received. A stop bit error is detected after a data frame is received, and the UART_RX_CTL.DROP_ON_FRAME_ERROR field specifies whether the received frame is dropped or send to the RX FIFO. If UART_RX_CTL.DROP_ON_FRAME_ERROR is '1', the received data frame is dropped. If UART_RX_CTL.DROP_ON_FRAME_ERROR is '0', the received data frame is send to the RX FIFO. Note that Firmware can only identify the erroneous data frame in the RX FIFO if it is fast enough to read the data frame before the hardware writes a next data frame into the RX FIFO; i.e. the RX FIFO does not have error flags to tag erroneous data frames. Default Value: 0
7	BLOCKED	SW cannot get access to the EZ memory (EZ_DATA accesses), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'. Default Value: 0
6	UNDERFLOW	Attempt to read from an empty RX FIFO. Only used in FIFO mode. Default Value: 0
5	OVERFLOW	Attempt to write to a full RX FIFO. Note: in I2C mode, the OVERFLOW is set when a data frame is received and the RX FIFO is full, independent of whether it is ACK'd or NACK'd. Only used in FIFO mode. Default Value: 0
3	FULL	RX FIFO is full. Note that received data frames are lost when the RX FIFO is full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is "0": # entries == FF_DATA_NR. MEM_WIDTH is "1": # entries == FF_DATA_NR/2. MEM_WIDTH is "2": # entries == FF_DATA_NR/4. Only used in FIFO mode. Default Value: 0
2	NOT_EMPTY	RX FIFO is not empty. Only used in FIFO mode. Default Value: 0
0	TRIGGER	More entries in the RX FIFO than the value specified by RX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode. Default Value: 0

9.1.50 SCB0_INTR_RX_SET

Receiver interrupt set request

Address: 0x40240FC4

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	None	RW1S	RW1S	None	RW1S
HW Access	A	A	A	None	A	A	None	A
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW1S	RW1S	RW1S	RW1S
HW Access	None				A	A	A	A
Name	None [15:12]				BREAK_DETECT	BAUD_DETECT	PARITY_ERROR	FRAME_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11	BREAK_DETECT	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
10	BAUD_DETECT	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
9	PARITY_ERROR	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
8	FRAME_ERROR	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
7	BLOCKED	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
6	UNDERFLOW	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
5	OVERFLOW	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
3	FULL	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
2	NOT_EMPTY	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
0	TRIGGER	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.51 SCB0_INTR_RX_MASK

Receiver interrupt mask

Address: 0x40240FC8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	None	RW	RW	None	RW
HW Access	R	R	R	None	R	R	None	R
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None				RW	RW	RW	RW
HW Access	None				R	R	R	R
Name	None [15:12]				BREAK_DETECT	BAUD_DETECT	PARITY_ERROR	FRAME_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11	BREAK_DETECT	Mask bit for corresponding bit in interrupt request register. Default Value: 0
10	BAUD_DETECT	Mask bit for corresponding bit in interrupt request register. Default Value: 0
9	PARITY_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
8	FRAME_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
7	BLOCKED	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
3	FULL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	NOT_EMPTY	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.52 SCB0_INTR_RX_MASKED

Receiver interrupt masked request

Address: 0x40240FCC

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	None	R	R	None	R
HW Access	W	W	W	None	W	W	None	W
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None				R	R	R	R
HW Access	None				W	W	W	W
Name	None [15:12]				BREAK_DETECT	BAUD_DETECT	PARITY_ERROR	FRAME_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
11	BREAK_DETECT	Logical and of corresponding request and mask bits. Default Value: 0
10	BAUD_DETECT	Logical and of corresponding request and mask bits. Default Value: 0
9	PARITY_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
8	FRAME_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
7	BLOCKED	Logical and of corresponding request and mask bits. Default Value: 0
6	UNDERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
5	OVERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
3	FULL	Logical and of corresponding request and mask bits. Default Value: 0
2	NOT_EMPTY	Logical and of corresponding request and mask bits. Default Value: 0
0	TRIGGER	Logical and of corresponding request and mask bits. Default Value: 0

9.1.53 SCB1_INTR_CAUSE

Active clocked interrupt signal

Address: 0x40250E00

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R	R	R	R	R
HW Access	None			W	W	W	W	W
Name	None [7:5]			I2C_EC	RX	TX	S	M

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
4	I2C_EC	Externally clock I2C interrupt active ("interrupt_i2c_ec"): INTR_I2C_EC_MASKED != 0. Default Value: 0
3	RX	Receiver interrupt active ("interrupt_rx"): INTR_RX_MASKED != 0. Default Value: 0
2	TX	Transmitter interrupt active ("interrupt_tx"): INTR_TX_MASKED != 0. Default Value: 0
1	S	Slave interrupt active ("interrupt_slave"): INTR_S_MASKED != 0. Default Value: 0
0	M	Master interrupt active ("interrupt_master"): INTR_M_MASKED != 0. Default Value: 0

9.1.54 SCB1_INTR_M

Master interrupt request

Address: 0x40250F00

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW1C	None	RW1C	RW1C	RW1C
HW Access	None			RW1S	None	RW1S	RW1S	RW1S
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1C
HW Access	None							RW1S
Name	None [15:9]							I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	I2C_BUS_ERROR	I2C master bus error (unexpected detection of START or STOP condition). Default Value: 0
4	I2C_STOP	I2C master STOP. Set to '1', when the master has transmitted a STOP. Default Value: 0
2	I2C_ACK	I2C master acknowledgement. Set to '1', when the master receives a ACK (typically after the master transmitted the slave address or TX data). Default Value: 0
1	I2C_NACK	I2C master negative acknowledgement. Set to '1', when the master receives a NACK (typically after the master transmitted the slave address or TX data). Default Value: 0
0	I2C_ARB_LOST	I2C master lost arbitration: the value driven by the master on the SDA line is not the same as the value observed on the SDA line. The Firmware should clear the TX FIFO, to re-do this transfer. Default Value: 0

9.1.55 SCB1_INTR_M_SET

Master interrupt set request

Address: 0x40250F04

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW1S	None	RW1S	RW1S	RW1S
HW Access	None			A	None	A	A	A
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1S
HW Access	None							A
Name	None [15:9]							I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	I2C_BUS_ERROR	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.56 SCB1_INTR_M_MASK

Master interrupt mask

Address: 0x40250F08

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	None	RW	RW	RW
HW Access	None			R	None	R	R	R
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	I2C_BUS_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.57 SCB1_INTR_M_MASKED

Master interrupt masked request

Address: 0x40250F0C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			R	None	R	R	R
HW Access	None			W	None	W	W	W
Name	None [7:5]			I2C_STOP	None	I2C_ACK	I2C_NACK	I2C_ARB_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							I2C_BUS_ERROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
8	I2C_BUS_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
4	I2C_STOP	Logical and of corresponding request and mask bits. Default Value: 0
2	I2C_ACK	Logical and of corresponding request and mask bits. Default Value: 0
1	I2C_NACK	Logical and of corresponding request and mask bits. Default Value: 0
0	I2C_ARB_LOST	Logical and of corresponding request and mask bits. Default Value: 0

9.1.58 SCB1_INTR_S

Slave interrupt request

Address: 0x40250F40

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C
HW Access	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1C
HW Access	None							RW1S
Name	None [15:9]							I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW1C
HW Access	None							RW1S
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	I2C slave RESTART received. Set to '1', when REPEATED START event is detected. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') AND clock stretching is performed (I2C_CTRL.S_NOT_READY_ADDR_NACK is '0'), this field is NOT set. this is not applicable when address in previous transfer is master-code. Default Value: 0
8	I2C_BUS_ERROR	I2C slave bus error (unexpected detection of START or STOP condition). This should not occur, it represents erroneous I2C bus behavior. In case of a bus error, the I2C slave state machine abort the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error. Default Value: 0
7	I2C_GENERAL	I2C slave general call address received. If CTRL.ADDR_ACCEPT, the received address 0x00 (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected. Default Value: 0
6	I2C_ADDR_MATCH	I2C slave matching address received. If CTRL.ADDR_ACCEPT, the received address (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected. Default Value: 0

9.1.58 SCB1_INTR_S (continued)

5	I2C_START	I2C slave START received. Set to '1', when START or REPEATED START event is detected. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') AND clock stretching is performed (I2C_CTRL.S_NOT_READY_ADDR_NACK is '0'), this field is NOT set. The Firmware should use INTR_S_EC.WAKE_UP, INTR_S.I2C_ADDR_MATCH and INTR_S.I2C_GENERAL. Default Value: 0
4	I2C_STOP	I2C STOP event for I2C (read or write) transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. The event is detected on any I2C transfer intended for this slave. Note that a I2C address intended for the slave (address is matching) will result in a I2C_STOP event independent of whether the I2C address is ACK'd or NACK'd. this is not applicable when address in previous transfer is master-code. Default Value: 0
3	I2C_WRITE_STOP	I2C STOP event for I2C write transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. In non EZ mode, the event is detected on any I2C write transfer intended for this slave. Note that a I2C write address intended for the slave (address is matching and a it is a write transfer) will result in a I2C_WRITE_STOP event independent of whether the I2C address is ACK'd or NACK'd. In EZ mode, the event is detected only on I2C write transfers that have EZ data written to the memory structure (an I2C write transfer that only communicates an I2C address and EZ address, will not result in this event being detected). this is not applicable when address in previous transfer is master-code. Default Value: 0
2	I2C_ACK	I2C slave acknowledgement received. Set to '1', when the slave receives a ACK (typically after the slave transmitted TX data). Default Value: 0
1	I2C_NACK	I2C slave negative acknowledgement received. Set to '1', when the slave receives a NACK (typically after the slave transmitted TX data). Default Value: 0
0	I2C_ARB_LOST	I2C slave lost arbitration: the value driven on the SDA line is not the same as the value observed on the SDA line (while the SCL line is '1'). This should not occur, it represents erroneous I2C bus behavior. In case of lost arbitration, the I2C slave state machine aborts the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error. Default Value: 0

9.1.59 SCB1_INTR_S_SET

Slave interrupt set request

Address: 0x40250F44

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
HW Access	A	A	A	A	A	A	A	A
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW1S
HW Access	None							A
Name	None [15:9]							I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW1S
HW Access	None							A
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
7	I2C_GENERAL	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
6	I2C_ADDR_MATCH	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
5	I2C_START	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
3	I2C_WRITE_STOP	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.60 SCB1_INTR_S_MASK

Slave interrupt mask

Address: 0x40250F48

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	RW	RW	RW	RW	RW
HW Access	R	R	R	R	R	R	R	R
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							RW
HW Access	None							R
Name	None [15:9]							I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							RW
HW Access	None							R
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Mask bit for corresponding bit in interrupt request register. Default Value: 0
8	I2C_BUS_ERROR	Mask bit for corresponding bit in interrupt request register. Default Value: 0
7	I2C_GENERAL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	I2C_ADDR_MATCH	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	I2C_START	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	I2C_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
3	I2C_WRITE_STOP	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	I2C_ACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	I2C_NACK	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	I2C_ARB_LOST	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.61 SCB1_INTR_S_MASKED

Slave interrupt masked request

Address: 0x40250F4C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	R	R	R	R	R
HW Access	W	W	W	W	W	W	W	W
Name	I2C_GEN- ERAL	I2C_AD- DR_MATCH	I2C_START	I2C_STOP	I2C_WRITE _STOP	I2C_ACK	I2C_NACK	I2C_AR- B_LOST

Bits	15	14	13	12	11	10	9	8
SW Access	None							R
HW Access	None							W
Name	None [15:9]							I2C_BUS_E RROR

Bits	23	22	21	20	19	18	17	16
SW Access	None							R
HW Access	None							W
Name	None [23:17]							I2C_RE- START

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	I2C_RESTART	Logical and of corresponding request and mask bits. Default Value: 0
8	I2C_BUS_ERROR	Logical and of corresponding request and mask bits. Default Value: 0
7	I2C_GENERAL	Logical and of corresponding request and mask bits. Default Value: 0
6	I2C_ADDR_MATCH	Logical and of corresponding request and mask bits. Default Value: 0
5	I2C_START	Logical and of corresponding request and mask bits. Default Value: 0
4	I2C_STOP	Logical and of corresponding request and mask bits. Default Value: 0
3	I2C_WRITE_STOP	Logical and of corresponding request and mask bits. Default Value: 0
2	I2C_ACK	Logical and of corresponding request and mask bits. Default Value: 0
1	I2C_NACK	Logical and of corresponding request and mask bits. Default Value: 0
0	I2C_ARB_LOST	Logical and of corresponding request and mask bits. Default Value: 0

9.1.62 SCB1_INTR_TX

Transmitter interrupt request

Address: 0x40250F80

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	RW1C	None		RW1C	RW1C
HW Access	RW1S	RW1S	RW1S	RW1S	None		RW1S	RW1S
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	SW cannot get access to the EZ memory (EZ data access), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'. Default Value: 0
6	UNDERFLOW	Attempt to read from an empty TX FIFO. This happens when SCB is ready to transfer data and EMPTY is '1'. Only used in FIFO mode. Default Value: 0
5	OVERFLOW	Attempt to write to a full TX FIFO. Only used in FIFO mode. Default Value: 0
4	EMPTY	TX FIFO is empty; i.e. it has 0 entries. Only used in FIFO mode. Default Value: 0
1	NOT_FULL	TX FIFO is not full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is "0": # entries != FF_DATA_NR. MEM_WIDTH is "1": # entries != FF_DATA_NR/2. MEM_WIDTH is "2": # entries != FF_DATA_NR/4. Only used in FIFO mode. Default Value: 0

9.1.62 SCB1_INTR_TX (continued)

0	TRIGGER	Less entries in the TX FIFO than the value specified by TX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode. Default Value: 0
---	---------	--

9.1.63 SCB1_INTR_TX_SET

Transmitter interrupt set request

Address: 0x40250F84

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	RW1S	None		RW1S	RW1S
HW Access	A	A	A	A	None		A	A
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
4	EMPTY	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
1	NOT_FULL	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.64 SCB1_INTR_TX_MASK

Transmitter interrupt mask

Address: 0x40250F88

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	RW	None		RW	RW
HW Access	R	R	R	R	None		R	R
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
4	EMPTY	Mask bit for corresponding bit in interrupt request register. Default Value: 0
1	NOT_FULL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.65 SCB1_INTR_TX_MASKED

Transmitter interrupt masked request

Address: 0x40250F8C

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	R	None		R	R
HW Access	W	W	W	W	None		W	W
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	EMPTY	None [3:2]		NOT_FULL	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Logical and of corresponding request and mask bits. Default Value: 0
6	UNDERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
5	OVERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
4	EMPTY	Logical and of corresponding request and mask bits. Default Value: 0
1	NOT_FULL	Logical and of corresponding request and mask bits. Default Value: 0
0	TRIGGER	Logical and of corresponding request and mask bits. Default Value: 0

9.1.66 SCB1_INTR_RX

Receiver interrupt request

Address: 0x40250FC0

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C	RW1C	RW1C	None	RW1C	RW1C	None	RW1C
HW Access	RW1S	RW1S	RW1S	None	RW1S	RW1S	None	RW1S
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	SW cannot get access to the EZ memory (EZ_DATA accesses), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'. Default Value: 0
6	UNDERFLOW	Attempt to read from an empty RX FIFO. Only used in FIFO mode. Default Value: 0
5	OVERFLOW	Attempt to write to a full RX FIFO. Note: in I2C mode, the OVERFLOW is set when a data frame is received and the RX FIFO is full, independent of whether it is ACK'd or NACK'd. Only used in FIFO mode. Default Value: 0
3	FULL	RX FIFO is full. Note that received data frames are lost when the RX FIFO is full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is "0": # entries == FF_DATA_NR. MEM_WIDTH is "1": # entries == FF_DATA_NR/2. MEM_WIDTH is "2": # entries == FF_DATA_NR/4. Only used in FIFO mode. Default Value: 0
2	NOT_EMPTY	RX FIFO is not empty. Only used in FIFO mode. Default Value: 0

9.1.66 SCB1_INTR_RX (continued)

0	TRIGGER	More entries in the RX FIFO than the value specified by RX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode. Default Value: 0
---	---------	--

9.1.67 SCB1_INTR_RX_SET

Receiver interrupt set request

Address: 0x40250FC4

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S	RW1S	RW1S	None	RW1S	RW1S	None	RW1S
HW Access	A	A	A	None	A	A	None	A
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
6	UNDERFLOW	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
5	OVERFLOW	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
3	FULL	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
2	NOT_EMPTY	Write with '1' to set corresponding bit in interrupt status register. Default Value: 0
0	TRIGGER	Write with '1' to set corresponding bit in interrupt request register. Default Value: 0

9.1.68 SCB1_INTR_RX_MASK

Receiver interrupt mask

Address: 0x40250FC8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW	RW	RW	None	RW	RW	None	RW
HW Access	R	R	R	None	R	R	None	R
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Mask bit for corresponding bit in interrupt request register. Default Value: 0
6	UNDERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
5	OVERFLOW	Mask bit for corresponding bit in interrupt request register. Default Value: 0
3	FULL	Mask bit for corresponding bit in interrupt request register. Default Value: 0
2	NOT_EMPTY	Mask bit for corresponding bit in interrupt request register. Default Value: 0
0	TRIGGER	Mask bit for corresponding bit in interrupt request register. Default Value: 0

9.1.69 SCB1_INTR_RX_MASKED

Receiver interrupt masked request

Address: 0x40250FCC

Retention: Not Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R	R	R	None	R	R	None	R
HW Access	W	W	W	None	W	W	None	W
Name	BLOCKED	UNDER-FLOW	OVER-FLOW	None	FULL	NOT_EMPTY	None	TRIGGER

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7	BLOCKED	Logical and of corresponding request and mask bits. Default Value: 0
6	UNDERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
5	OVERFLOW	Logical and of corresponding request and mask bits. Default Value: 0
3	FULL	Logical and of corresponding request and mask bits. Default Value: 0
2	NOT_EMPTY	Logical and of corresponding request and mask bits. Default Value: 0
0	TRIGGER	Logical and of corresponding request and mask bits. Default Value: 0

CAPSENSE™ registers**10 CAPSENSE™ registers**

Note: Infineon recommends to use the CAPSENSE™ middleware provided by the ModusToolbox™ IDE to implement CAPSENSE™ designs. See the [PSOC™ 4 and PSOC™ 6 MCU CAPSENSE™ design guide](#) for more details.

It is not recommended to directly access or modify CAPSENSE™ registers. If you want to create custom register settings, contact technical support.

Cortex M0+ (CM0P) registers

11 Cortex M0+ (CM0P) registers

This section discusses the CM0+ registers. It lists all the registers in mapping tables, in address order.

11.1 Register details

Register	Address	Description
CM0P_DWT_PID4	0xE0001FD0	Watchpoint Unit CoreSight ROM Table Peripheral ID #4
CM0P_DWT_PID0	0xE0001FE0	Watchpoint Unit CoreSight ROM Table Peripheral ID #0
CM0P_DWT_PID1	0xE0001FE4	Watchpoint Unit CoreSight ROM Table Peripheral ID #1
CM0P_DWT_PID2	0xE0001FE8	Watchpoint Unit CoreSight ROM Table Peripheral ID #2
CM0P_DWT_PID3	0xE0001FEC	Watchpoint Unit CoreSight ROM Table Peripheral ID #3
CM0P_DWT_CID0	0xE0001FF0	Watchpoint Unit CoreSight ROM Table Component ID #0
CM0P_DWT_CID1	0xE0001FF4	Watchpoint Unit CoreSight ROM Table Component ID #1
CM0P_DWT_CID2	0xE0001FF8	Watchpoint Unit CoreSight ROM Table Component ID #2
CM0P_DWT_CID3	0xE0001FFC	Watchpoint Unit CoreSight ROM Table Component ID #3
CM0P_BP_PID4	0xE0002FD0	Breakpoint Unit CoreSight ROM Table Peripheral ID #4
CM0P_BP_PID0	0xE0002FE0	Breakpoint Unit CoreSight ROM Table Peripheral ID #0
CM0P_BP_PID1	0xE0002FE4	Breakpoint Unit CoreSight ROM Table Peripheral ID #1
CM0P_BP_PID2	0xE0002FE8	Breakpoint Unit CoreSight ROM Table Peripheral ID #2
CM0P_BP_PID3	0xE0002FEC	Breakpoint Unit CoreSight ROM Table Peripheral ID #3
CM0P_BP_CID0	0xE0002FF0	Breakpoint Unit CoreSight ROM Table Component ID #0
CM0P_BP_CID1	0xE0002FF4	Breakpoint Unit CoreSight ROM Table Component ID #1
CM0P_BP_CID2	0xE0002FF8	Breakpoint Unit CoreSight ROM Table Component ID #2
CM0P_BP_CID3	0xE0002FFC	Breakpoint Unit CoreSight ROM Table Component ID #3
CM0P_SYST_CSR	0xE000E010	SysTick Control & Status
CM0P_SYST_RVR	0xE000E014	SysTick Reload Value
CM0P_SYST_CVR	0xE000E018	SysTick Current Value
CM0P_SYST_CALIB	0xE000E01C	SysTick Calibration Value
CM0P_ISER	0xE000E100	Interrupt Set-Enable Register
CM0P_ICER	0xE000E180	Interrupt Clear Enable Register
CM0P_ISPR	0xE000E200	Interrupt Set-Pending Register
CM0P_ICPR	0xE000E280	Interrupt Clear-Pending Register
CM0P_IPR0	0xE000E400	Interrupt Priority Registers
CM0P_IPR1	0xE000E404	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_IPR2	0xE000E408	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_IPR3	0xE000E40C	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_IPR4	0xE000E410	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_IPR5	0xE000E414	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_IPR6	0xE000E418	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.

Cortex M0+ (CM0P) registers

Register	Address	Description
CM0P_IPR7	0xE000E41C	Interrupt Priority Registers. See CM0P_IPR0 for the details of bit fields.
CM0P_CPUID	0xE000ED00	CPUID Register
CM0P_ICSR	0xE000ED04	Interrupt Control State Register
CM0P_VTOR	0xE000ED08	Vector Table Offset Register
CM0P_AIRCR	0xE000ED0C	Application Interrupt and Reset Control Register
CM0P_SCR	0xE000ED10	System Control Register
CM0P_CCR	0xE000ED14	Configuration and Control Register
CM0P_SHPR2	0xE000ED1C	System Handler Priority Register 2
CM0P_SHPR3	0xE000ED20	System Handler Priority Register 3
CM0P_SHCSR	0xE000ED24	System Handler Control and State Register
CM0P_SCS_PID4	0xE000EFD0	System Control Space ROM Table Peripheral ID #4
CM0P_SCS_PID0	0xE000EFE0	System Control Space ROM Table Peripheral ID #0
CM0P_SCS_PID1	0xE000EFE4	System Control Space ROM Table Peripheral ID #1
CM0P_SCS_PID2	0xE000EFE8	System Control Space ROM Table Peripheral ID #2
CM0P_SCS_PID3	0xE000EFEC	System Control Space ROM Table Peripheral ID #3
CM0P_SCS_CID0	0xE000EFF0	System Control Space ROM Table Component ID #0
CM0P_SCS_CID1	0xE000EFF4	System Control Space ROM Table Component ID #1
CM0P_SCS_CID2	0xE000EFF8	System Control Space ROM Table Component ID #2
CM0P_SCS_CID3	0xE000EFFC	System Control Space ROM Table Component ID #3
CM0P_ROM_SCS	0xE00FF000	CM0+ CoreSight ROM Table Peripheral #0
CM0P_ROM_DWT	0xE00FF004	CM0+ CoreSight ROM Table Peripheral #1
CM0P_ROM_BPU	0xE00FF008	CM0+ CoreSight ROM Table Peripheral #2
CM0P_ROM_END	0xE00FF00C	CM0+ CoreSight ROM Table End Marker
CM0P_ROM_CSMT	0xE00FF0CC	CM0+ CoreSight ROM Table Memory Type
CM0P_ROM_PID4	0xE00FFFD0	CM0+ CoreSight ROM Table Peripheral ID #4
CM0P_ROM_PID0	0xE00FFFE0	CM0+ CoreSight ROM Table Peripheral ID #0
CM0P_ROM_PID1	0xE00FFFE4	CM0+ CoreSight ROM Table Peripheral ID #1
CM0P_ROM_PID2	0xE00FFFE8	CM0+ CoreSight ROM Table Peripheral ID #2
CM0P_ROM_PID3	0xE00FF FEC	CM0+ CoreSight ROM Table Peripheral ID #3
CM0P_ROM_CID0	0xE00FFFF0	CM0+ CoreSight ROM Table Component ID #0
CM0P_ROM_CID1	0xE00FFFF4	CM0+ CoreSight ROM Table Component ID #1
CM0P_ROM_CID2	0xE00FFFF8	CM0+ CoreSight ROM Table Component ID #2
CM0P_ROM_CID3	0xE00FFFFC	CM0+ CoreSight ROM Table Component ID #3

11.1.1 CM0P_DWT_PID4

Watchpoint Unit CoreSight ROM Table Peripheral ID #4

Address: 0xE0001FD0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #4 Default Value: 4

11.1.2 CM0P_DWT_PID0

Watchpoint Unit CoreSight ROM Table Peripheral ID #0

Address: 0xE0001FE0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #0 Default Value: 10

11.1.3 CM0P_DWT_PID1

Watchpoint Unit CoreSight ROM Table Peripheral ID #1

Address: 0xE0001FE4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #1 Default Value: 176

11.1.4 CM0P_DWT_PID2

Watchpoint Unit CoreSight ROM Table Peripheral ID #2

Address: 0xE0001FE8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #2 Default Value: 11

11.1.5 CM0P_DWT_PID3

Watchpoint Unit CoreSight ROM Table Peripheral ID #3

Address: 0xE0001FEC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #3 Default Value: 0

11.1.6 CM0P_DWT_CID0

Watchpoint Unit CoreSight ROM Table Component ID #0

Address: 0xE0001FF0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #0 Default Value: 13

11.1.7 CM0P_DWT_CID1

Watchpoint Unit CoreSight ROM Table Component ID #1

Address: 0xE0001FF4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #1 Default Value: 224

11.1.8 CM0P_DWT_CID2

Watchpoint Unit CoreSight ROM Table Component ID #2

Address: 0xE0001FF8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #2 Default Value: 5

11.1.9 CM0P_DWT_CID3

Watchpoint Unit CoreSight ROM Table Component ID #3

Address: 0xE0001FFC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #3 Default Value: 177

11.1.10 CM0P_BP_PID4

Breakpoint Unit CoreSight ROM Table Peripheral ID #4

Address: 0xE0002FD0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #4 Default Value: 4

11.1.11 CM0P_BP_PID0

Breakpoint Unit CoreSight ROM Table Peripheral ID #0

Address: 0xE0002FE0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #0 Default Value: 11

11.1.12 CM0P_BP_PID1

Breakpoint Unit CoreSight ROM Table Peripheral ID #1

Address: 0xE0002FE4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #1 Default Value: 176

11.1.13 CM0P_BP_PID2

Breakpoint Unit CoreSight ROM Table Peripheral ID #2

Address: 0xE0002FE8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #2 Default Value: 11

11.1.14 CM0P_BP_PID3

Breakpoint Unit CoreSight ROM Table Peripheral ID #3

Address: 0xE0002FEC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #3 Default Value: 0

11.1.15 CM0P_BP_CID0

Breakpoint Unit CoreSight ROM Table Component ID #0

Address: 0xE0002FF0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #0 Default Value: 13

11.1.16 CM0P_BP_CID1

Breakpoint Unit CoreSight ROM Table Component ID #1

Address: 0xE0002FF4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #1 Default Value: 224

11.1.17 CM0P_BP_CID2

Breakpoint Unit CoreSight ROM Table Component ID #2

Address: 0xE0002FF8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #2 Default Value: 5

11.1.18 CM0P_BP_CID3

Breakpoint Unit CoreSight ROM Table Component ID #3

Address: 0xE0002FFC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #3 Default Value: 177

11.1.19 CM0P_SYST_CSR

SysTick Control & Status

Address: 0xE000E010

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW	RW	RW
HW Access	None					R	R	R
Name	None [7:3]					CLK-SOURCE	TICKINT	ENABLE

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							R
HW Access	None							RW
Name	None [23:17]							COUNT-FLAG

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
16	COUNTFLAG	Indicates whether the counter has counted to "0" since the last read of this register: '0': counter has not counted to "0". '1': counter has counted to "0". COUNTFLAG is set to '1' by a count transition from "1" to "0". COUNTFLAG is cleared to '0' by a read of this register, and by any write to the SYST_CVR register. Default Value: 0
2	CLKSOURCE	Indicates the SysTick counter clock source: '0': SysTick uses the low frequency clock "clk_lf". For this mode to function, "clk_lf" should be less than half the frequency of "clk_sys". Note that "clk_lf" is generated by a low accuracy ILO (Internal Low power Oscillator), with a target frequency of 32.768 kHz (frequency can be as low as 15 kHz and as high as 60 kHz). '1': SysTick uses the system/processor clock "clk_sys". If SysTick counter functionality is not present in the device. This field should be set to '1', such that SysTick uses the system clock "clk_sys". Default Value: 0

11.1.19 CM0P_SYST_CSR (continued)

1	TICKINT	Indicates whether counting to "0" causes the status of the SysTick exception to change to pending: '0': count to "0" does not affect the SysTick exception status. '1': count to "0" changes the SysTick exception status to pending. Changing the value of the counter to "0" by writing zero to the SYST_CVR register to "0" never changes the status of the SysTick exception. Default Value: 0
0	ENABLE	Indicates the enabled status of the SysTick counter: '0': counter is disabled. '1': counter is operating. Default Value: 0

11.1.20 CM0P_SYST_RVR

SysTick Reload Value

Address: 0xE000E014

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	RELOAD [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	RELOAD [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	RELOAD [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 0	RELOAD	The value to load into the SYST_CVR register when the counter reaches 0. Default Value: X

11.1.21 CM0P_SYST_CVR

SysTick Current Value

Address: 0xE000E018

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW							
HW Access	R							
Name	CURRENT [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	CURRENT [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	CURRENT [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
23 : 0	CURRENT	Current counter value. This is the value of the counter at the time it is sampled. Default Value: X

11.1.22 CM0P_SYST_CALIB

SysTick Calibration Value

Address: 0xE000E01C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	RW							
Name	TENMS [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	RW							
Name	TENMS [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	RW							
Name	TENMS [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R	R	None					
HW Access		RW	None					
Name	NOREF	SKEW	None [29:24]					

Bits	Name	Description
31	NOREF	Indicates whether a implementation defined reference clock is provided: '0': the reference clock is provided. '1': the reference clock is not provided. When this bit is '1', the SYST_CSR.CLKSOURCEis forced to '1' and cannot be cleared to '0'. SysTick counter functionality on the low frequency clock is provided and this field is '0'. Default Value: 0
30	SKEW	Indicates whether the 10ms calibration value is exact: '0': 10ms calibration value is exact. '1': 10ms calibration value is inexact, because of the clock frequency. SysTick counter functionality on the low frequency clock is provided and this field is '1' (due to the low accuracy ILO). Default Value: X
23 : 0	TENMS	Optionally, holds a reload value to be used for 10ms (100Hz) timing, subject to system clock skew errors. If this field is "0", the calibration value is not known. SysTick counter functionality on the low frequency clock is provided and this field is 0x00:00147. Default Value: X

11.1.23 CM0P_ISER

Interrupt Set-Enable Register

Address: 0xE000E100

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S							
HW Access	R							
Name	SETENA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW1S							
HW Access	R							
Name	SETENA [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW1S							
HW Access	R							
Name	SETENA [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW1S							
HW Access	R							
Name	SETENA [31:24]							

Bits	Name	Description
31 : 0	SETENA	Enables, or reads the enabled state of one or more interrupts. Each bit corresponds to the same numbered interrupt. Default Value: 0

11.1.24 CM0P_ICER

Interrupt Clear Enable Register

Address: 0xE000E180

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C							
HW Access	R							
Name	CLRENA [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW1C							
HW Access	R							
Name	CLRENA [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW1C							
HW Access	R							
Name	CLRENA [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW1C							
HW Access	R							
Name	CLRENA [31:24]							

Bits	Name	Description
31 : 0	CLRENA	Disables, or reads the enabled state of one or more interrupts. Each bit corresponds to the same numbered interrupt. Default Value: 0

11.1.25 CM0P_ISPR

Interrupt Set-Pending Register

Address: 0xE000E200

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1S							
HW Access	R							
Name	SETPEND [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW1S							
HW Access	R							
Name	SETPEND [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW1S							
HW Access	R							
Name	SETPEND [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW1S							
HW Access	R							
Name	SETPEND [31:24]							

Bits	Name	Description
31 : 0	SETPEND	Changes the state of one or more interrupts to pending. Each bit corresponds to the same numbered interrupt. Default Value: 0

11.1.26 CM0P_ICPR

Interrupt Clear-Pending Register

Address: 0xE000E280

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW1C							
HW Access	R							
Name	CLRPEND [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW1C							
HW Access	R							
Name	CLRPEND [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW1C							
HW Access	R							
Name	CLRPEND [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW1C							
HW Access	R							
Name	CLRPEND [31:24]							

Bits	Name	Description
31 : 0	CLRPEND	Changes the state of one or more interrupts to not pending. Each bit corresponds to the same numbered interrupt. Default Value: 0

11.1.27 CM0P_IPR0

Interrupt Priority Registers

Address: 0xE000E400

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	RW		None					
HW Access	R		None					
Name	PRI_N0 [7:6]		None [5:0]					

Bits	15	14	13	12	11	10	9	8
SW Access	RW		None					
HW Access	R		None					
Name	PRI_N1 [15:14]		None [13:8]					

Bits	23	22	21	20	19	18	17	16
SW Access	RW		None					
HW Access	R		None					
Name	PRI_N2 [23:22]		None [21:16]					

Bits	31	30	29	28	27	26	25	24
SW Access	RW		None					
HW Access	R		None					
Name	PRI_N3 [31:30]		None [29:24]					

Bits	Name	Description
31 : 30	PRI_N3	Priority of interrupt number N+3. Default Value: 0
23 : 22	PRI_N2	Priority of interrupt number N+2. Default Value: 0
15 : 14	PRI_N1	Priority of interrupt number N+1. Default Value: 0
7 : 6	PRI_N0	Priority of interrupt number N. Default Value: 0

11.1.28 CM0P_CPUID

CPUID Register

Address: 0xE000ED00

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R				R			
HW Access								
Name	PARTNO [7:4]				REVISION [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	PARTNO [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R				R			
HW Access								
Name	VARIANT [23:20]				CONSTANT [19:16]			

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	IMPLEMENTER [31:24]							

Bits	Name	Description
31 : 24	IMPLEMENTER	Implementer code for ARM. Default Value: 65
23 : 20	VARIANT	Implementation defined. In ARM implementations this is the major revision number n in the rn part of the mpm revision status, Product revision status on page xii. Default Value: 0
19 : 16	CONSTANT	Indicates the architecture, ARMv6-M Default Value: 12
15 : 4	PARTNO	Indicates part number, Cortex-M0+ Default Value: 3168
3 : 0	REVISION	Indicates revision. In ARM implementations this is the minor revision number n in the pn part of the mpm revision status, see Product revision status on page xii. For release r0p1. Default Value: 1

11.1.29 CM0P_ICSR

Interrupt Control State Register

Address: 0xE000ED04

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	RW							
Name	VECTACTIVE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R				None			R
HW Access	RW				None			RW
Name	VECTPENDING [15:12]				None [11:9]			VECTACTIVE

Bits	23	22	21	20	19	18	17	16
SW Access	R	R	None	R				
HW Access	RW	RW	None	RW				
Name	ISRPRE-EMPT	ISRPENDING	None	VECTPENDING [20:16]				

Bits	31	30	29	28	27	26	25	24
SW Access	RW1S	None		RW1S	RW1C	RW1S	RW1C	None
HW Access	RW	None		RW	R	RW	R	None
Name	NMIPENDSET	None [30:29]		PENDSVSET	PENDSVCLR	PENDSTSETb	PENDSTCLR	None

Bits	Name	Description
31	NMIPENDSET	Activates an NMI exception or reads back the current state. Because NMI is the highest priority exception, it activates as soon as it is registered. Default Value: 0
28	PENDSVSET	Sets a pending PendSV interrupt or reads back the current state. Use this normally to request a context switch. Writing PENDSVSET and PENDSVCLR to '1' concurrently is UNPREDICTABLE. Default Value: 0
27	PENDSVCLR	Clears a pending PendSV interrupt. Default Value: 0
26	PENDSTSETb	Sets a pending SysTick or reads back the current state. Writing PENDSTSET and PENDSTCLR to '1' concurrently is UNPREDICTABLE. Default Value: 0
25	PENDSTCLR	Clears a pending SysTick, whether set here or by the timer hardware. Default Value: 0
23	ISRPREEMPT	Indicates whether a pending exception will be serviced on exit from debug halt state. Default Value: 0
22	ISRPENDING	Indicates if an external configurable, NVIC generated, interrupt is pending. Default Value: 0
20 : 12	VECTPENDING	The exception number for the highest priority pending exception. 0= No pending exceptions. The pending state includes the effect of memory-mapped enable and mask registers. It does not include the PRIMASK special-purpose register qualifier. Default Value: 0

11.1.29 CM0P_ICSR (continued)

8 : 0	VECTACTIVE	The exception number for the current executing exception. 0= Thread mode. This is the same value as IPSR[8:0] Default Value: 0
-------	------------	---

11.1.30 CM0P_VTOR

Vector Table Offset Register

Address: 0xE000ED08

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW							
HW Access	R							
Name	TBLOFF [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	TBLOFF [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access	R							
Name	TBLOFF [31:24]							

Bits	Name	Description
31 : 8	TBLOFF	Table offset address. All bits of the Vector table address that are not defined by the VTOR are zero. Default Value: 0

11.1.31 CM0P_AIRCR

Application Interrupt and Reset Control Register

Address: 0xE000ED0C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None					RW1S	RW1C	None
HW Access	None					R	R	None
Name	None [7:3]					SYSRESE- TREQ	VECTCL- RACTIVE	None

Bits	15	14	13	12	11	10	9	8
SW Access	R	None						
HW Access		None						
Name	ENDIAN- NESS	None [14:8]						

Bits	23	22	21	20	19	18	17	16
SW Access	RW							
HW Access	R							
Name	VECTKEY [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW							
HW Access	R							
Name	VECTKEY [31:24]							

Bits	Name	Description
31 : 16	VECTKEY	Vector Key. The value 0x05FA must be written to this register, otherwise the register write is UNPREDICTABLE. Readback value is UNKNOWN. Default Value: X
15	ENDIANNESS	Indicates the memory system data endianness: 0 little endian 1 big endian. See Endian support on page A3-44 for more information. Default Value: 0
2	SYSRESETREQ	System Reset Request. Writing 1 to this bit asserts a signal to request a reset by the external system. This will cause a full system reset of the CPU and all other components in the device. See Reset management on page B1-240 for more information. Default Value: 0
1	VECTCLRACTIVE	Clears all active state information for fixed and configurable exceptions. The effect of writing a 1 to this bit if the processor is not halted in Debug state is UNPREDICTABLE. Default Value: 0

11.1.32 CM0P_SCR

System Control Register

Address: 0xE000ED10

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None			RW	None	RW	RW	None
HW Access	None			R	None	R	R	None
Name	None [7:5]			SEVON- PEND	None	SLEEP- DEEP	SLEEPON- EXIT	None

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
4	SEVONPEND	Determines whether an interrupt transition from inactive state to pending state is a wakeup event: 0: transitions from inactive to pending are not wakeup events. 1: transitions from inactive to pending are wakeup events. See WFE on page A6-197 for more information. Default Value: 0
2	SLEEPDEEP	An implementation can use this bit to select DeepSleep/Hibernate power modes upon execution of WFI/WFE: 0: Select Sleep mode 1: Select DeepSleep/Hibernate (depends on PWR_CONTROL.HIBERNATE) Default Value: 0
1	SLEEPONEXIT	Determines whether, on an exit from an ISR that returns to the base level of execution priority, the processor enters a sleep state: 0 do not enter sleep state. 1 enter sleep state. See Power management on page B1-240 for more information. Default Value: 0

11.1.33 CM0P_CCR

Configuration and Control Register

Address: 0xE000ED14

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None				R	None		
HW Access	None					None		
Name	None [7:4]				UN- ALIGN_TR P	None		

Bits	15	14	13	12	11	10	9	8
SW Access	None						R	None
HW Access	None							None
Name	None [15:10]						STKALIGN	None

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
9	STKALIGN	1: On exception entry, the SP used prior to the exception is adjusted to be 8-byte aligned and the context to restore it is saved. The SP is restored on the associated exception return. Default Value: 1
3	UNALIGN_TRP	1: unaligned word and halfword accesses generate a HardFault exception. Default Value: 1

11.1.34 CM0P_SHPR2

System Handler Priority Register 2

Address: 0xE000ED1C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	RW		None					
HW Access	R		None					
Name	PRI_11 [31:30]		None [29:24]					

Bits	Name	Description
31 : 30	PRI_11	Priority of system handler 11, SVCALL Default Value: 0

11.1.35 CM0P_SHPR3

System Handler Priority Register 3

Address: 0xE000ED20

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	RW		None					
HW Access	R		None					
Name	PRI_14 [23:22]		None [21:16]					

Bits	31	30	29	28	27	26	25	24
SW Access	RW		None					
HW Access	R		None					
Name	PRI_15 [31:30]		None [29:24]					

Bits	Name	Description
31 : 30	PRI_15	Priority of system handler 15, SysTick Default Value: 0
23 : 22	PRI_14	Priority of system handler 14, PendSV Default Value: 0

11.1.36 CM0P_SHCSR

System Handler Control and State Register

Address: 0xE000ED24

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None							
HW Access	None							
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	RW	None						
HW Access	RW	None						
Name	SVCALL- PENDED	None						

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
15	SVCALLPENDED	0 SVCall is not pending. 1 SVCall is pending. This bit reflects the pending state on a read, and updates the pending state, to the value written, on a write. (Pending state bits are set to 1 when an exception occurs, and are cleared to 0 when an exception becomes active.) Default Value: 0

11.1.37 CM0P_SCS_PID4

System Control Space ROM Table Peripheral ID #4

Address: 0xE000EFD0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #4 Default Value: 4

11.1.38 CM0P_SCS_PID0

System Control Space ROM Table Peripheral ID #0

Address: 0xE000EFE0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #0 Default Value: 8

11.1.39 CM0P_SCS_PID1

System Control Space ROM Table Peripheral ID #1

Address: 0xE000EFE4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #1 Default Value: 176

11.1.40 CM0P_SCS_PID2

System Control Space ROM Table Peripheral ID #2

Address: 0xE000EFE8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #2 Default Value: 11

11.1.41 CM0P_SCS_PID3

System Control Space ROM Table Peripheral ID #3

Address: 0xE000EFEC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #3 Default Value: 0

11.1.42 CM0P_SCS_CID0

System Control Space ROM Table Component ID #0

Address: 0xE000EFF0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #0 Default Value: 13

11.1.43 CM0P_SCS_CID1

System Control Space ROM Table Component ID #1

Address: 0xE000EFF4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #1 Default Value: 224

11.1.44 CM0P_SCS_CID2

System Control Space ROM Table Component ID #2

Address: 0xE000EFF8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #2 Default Value: 5

11.1.45 CM0P_SCS_CID3

System Control Space ROM Table Component ID #3

Address: 0xE000E0FC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #3 Default Value: 177

11.1.46 CM0P_ROM_SCS

CM0+ CoreSight ROM Table Peripheral #0

Address: 0xE00FF000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Offset to SCS ROM Table Default Value: 4293980163

11.1.47 CM0P_ROM_DWT

CM0+ CoreSight ROM Table Peripheral #1

Address: 0xE00FF004

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Offset to DWT ROM Table Default Value: 4293926915

11.1.48 CM0P_ROM_BPU

CM0+ CoreSight ROM Table Peripheral #2

Address: 0xE00FF008

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Offset to BPU ROM Table Default Value: 4293931011

11.1.49 CM0P_ROM_END

CM0+ CoreSight ROM Table End Marker

Address: 0xE00FF00C

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	End marker in peripheral list Default Value: 0

11.1.50 CM0P_ROM_CSMT

CM0+ CoreSight ROM Table Memory Type

Address: 0xE00FFFCC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Memory Type Default Value: 1

11.1.51 CM0P_ROM_PID4

CM0+ CoreSight ROM Table Peripheral ID #4

Address: 0xE00FFFD0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #4 Default Value: 4

11.1.52 CM0P_ROM_PID0

CM0+ CoreSight ROM Table Peripheral ID #0

Address: 0xE00FFFE0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #0 Default Value: 192

11.1.53 CM0P_ROM_PID1

CM0+ CoreSight ROM Table Peripheral ID #1

Address: 0xE00FFE4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #1 Default Value: 180

11.1.54 CM0P_ROM_PID2

CM0+ CoreSight ROM Table Peripheral ID #2

Address: 0xE00FFE8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #2 Default Value: 11

11.1.55 CM0P_ROM_PID3

CM0+ CoreSight ROM Table Peripheral ID #3

Address: 0xE00FFEC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Peripheral ID #3 Default Value: 0

11.1.56 CM0P_ROM_CID0

CM0+ CoreSight ROM Table Component ID #0

Address: 0xE00FFF0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #0 Default Value: 13

11.1.57 CM0P_ROM_CID1

CM0+ CoreSight ROM Table Component ID #1

Address: 0xE00FFF4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #1 Default Value: 16

11.1.58 CM0P_ROM_CID2

CM0+ CoreSight ROM Table Component ID #2

Address: 0xE00FFF8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #2 Default Value: 5

11.1.59 CM0P_ROM_CID3

CM0+ CoreSight ROM Table Component ID #3

Address: 0xE00FFFC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access								
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access								
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access								
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access								
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component ID #3 Default Value: 177

ROM Table registers

12 ROM Table registers

This section discusses the ROM Table registers. It lists all the registers in mapping tables, in address order.

12.1 Register details

Register	Address	Description
ROMTABLE_ADDR	0xF0000000	Link to Cortex M0 ROM Table.
ROMTABLE_DID	0xF0000FCC	Device Type Identifier register.
ROMTABLE_PID4	0xF0000FD0	Peripheral Identification Register 4.
ROMTABLE_PID5	0xF0000FD4	Peripheral Identification Register 5.
ROMTABLE_PID6	0xF0000FD8	Peripheral Identification Register 6.
ROMTABLE_PID7	0xF0000FDC	Peripheral Identification Register 7.
ROMTABLE_PID0	0xF0000FE0	Peripheral Identification Register 0.
ROMTABLE_PID1	0xF0000FE4	Peripheral Identification Register 1.
ROMTABLE_PID2	0xF0000FE8	Peripheral Identification Register 2.
ROMTABLE_PID3	0xF0000FEC	Peripheral Identification Register 3.
ROMTABLE_CID0	0xF0000FF0	Component Identification Register 0.
ROMTABLE_CID1	0xF0000FF4	Component Identification Register 1.
ROMTABLE_CID2	0xF0000FF8	Component Identification Register 2.
ROMTABLE_CID3	0xF0000FFC	Component Identification Register 3.

12.1.1 ROMTABLE_ADDR

Link to Cortex M0 ROM Table.

Address: 0xF0000000

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	None						R	R
HW Access	None						R	R
Name	None [7:2]						FOR-MAT_32BIT	PRESENT

Bits	15	14	13	12	11	10	9	8
SW Access	R				None			
HW Access	R				None			
Name	ADDR_OFFSET [15:12]				None [11:8]			

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	ADDR_OFFSET [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	ADDR_OFFSET [31:24]							

Bits	Name	Description
31 : 12	ADDR_OFFSET	Address offset of the Cortex-M0 ROM Table base address (0xe00f:f000) wrt. Cypress chip specific ROM Table base address (0xf000:0000). ADDR_OFFSET[19:0] = 0xe00f:f - 0xf000:0 = 0xf00f:f. Default Value: 983295
1	FORMAT_32BIT	ROM Table format: '0': 8-bit format. '1': 32-bit format. Default Value: 1
0	PRESENT	Entry present. Default Value: 1

12.1.2 ROMTABLE_DID

Device Type Identifier register.

Address: 0xF0000FCC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	. Default Value: 1

12.1.3 ROMTABLE_PID4

Peripheral Identification Register 4.

Address: 0xF0000FD0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R				R			
HW Access	R				R			
Name	COUNT [7:4]				JEP_CONTINUATION [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	COUNT	Size of ROM Table is $2^{\text{COUNT}} \times 4$ KByte. Default Value: 0
3 : 0	JEP_CONTINUATION	JEP106 continuation code. This value is product specific and specified as part of the product definition in the CPUSS.JEPCONTINUATION parameter. Default Value: Undefined

12.1.4 ROMTABLE_PID5

Peripheral Identification Register 5.

Address: 0xF0000FD4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	. Default Value: 0

12.1.5 ROMTABLE_PID6

Peripheral Identification Register 6.

Address: 0xF0000FD8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	. Default Value: 0

12.1.6 ROMTABLE_PID7

Peripheral Identification Register 7.

Address: 0xF0000FDC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	. Default Value: 0

12.1.7 ROMTABLE_PID0

Peripheral Identification Register 0.

Address: 0xF0000FE0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	PN_MIN [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 0	PN_MIN	JEP106 part number. 4 lsbs of CPUSS.PARTNUMBER parameter. Default Value: Undefined

12.1.8 ROMTABLE_PID1

Peripheral Identification Register 1.

Address: 0xF0000FE4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R				R			
HW Access	R				R			
Name	JEPID_MIN [7:4]				PN_MAJ [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	JEPID_MIN	JEP106 vendor id. 4 lsbs of CPUSS.JEPID parameter. Default Value: Undefined
3 : 0	PN_MAJ	JEP106 part number. 4 msbs of CPUSS.PARTNUMBER parameter. Default Value: Undefined

12.1.9 ROMTABLE_PID2

Peripheral Identification Register 2.

Address: 0xF0000FE8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R				R			
HW Access	R				R			
Name	REV [7:4]				JEPID_MAJ [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	REV	Major REVision number (chip specific). Identifies the design iteration of the component. For first tape out: 0x1. This field is incremented on subsequent tape outs. Default Value: Undefined
3 : 0	JEPID_MAJ	JEP106 vendor id. 4 msbs of CPUSS.JEPID parameter. Default Value: Undefined

12.1.10 ROMTABLE_PID3

Peripheral Identification Register 3.

Address: 0xF0000FEC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R				R			
HW Access	R				R			
Name	REV_AND [7:4]				CM [3:0]			

Bits	15	14	13	12	11	10	9	8
SW Access	None							
HW Access	None							
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	None							
HW Access	None							
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	None							
HW Access	None							
Name	None [31:24]							

Bits	Name	Description
7 : 4	REV_AND	Minor REVision number (chip specific). For first tape out: 0x1. This field is incremented on subsequent tape outs. Default Value: Undefined
3 : 0	CM	Customer modified field. This field is used to track modifications to the original component design as a result of component IP reuse. Default Value: 0

12.1.11 ROMTABLE_CID0

Component Identification Register 0.

Address: 0xF0000FF0

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component identification byte 0 of 4-byte component identification 0xB105:100D. Default Value: 13

12.1.12 ROMTABLE_CID1

Component Identification Register 1.

Address: 0xF0000FF4

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component identification byte 1 of 4-byte component identification 0xB105:100D. Component class: "ROM Table". Default Value: 16

12.1.13 ROMTABLE_CID2

Component Identification Register 2.

Address: 0xF0000FF8

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component identification byte 2 of 4-byte component identification 0xB105:100D. Default Value: 5

12.1.14 ROMTABLE_CID3

Component Identification Register 3.

Address: 0xF0000FFC

Retention: Retained

Bits	7	6	5	4	3	2	1	0
SW Access	R							
HW Access	R							
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
SW Access	R							
HW Access	R							
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
SW Access	R							
HW Access	R							
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
SW Access	R							
HW Access	R							
Name	VALUE [31:24]							

Bits	Name	Description
31 : 0	VALUE	Component identification byte 3 of 4-byte component identification 0xB105:100D. Default Value: 177

Revision history
Revision history

Document version	Date of release	Description of changes
**	2022-01-25	Initial release.
*A	2022-05-13	Updated all the registers.
*B	2023-01-19	Added “Retention” register convention in “Register general conventions” on page 3. Updated “Supervisory Flash registers” on page 7 and “System Resources Subsystem (SRSS) registers” on page 47. Updated copyright information.
*C	2023-02-21	Updated “Supervisory Flash registers” on page 7 (SFLASH_MSCLP_CLK_IMO_TRIM registers).
*D	2023-08-03	Updated the following chapters: • “High Speed IO Matrix (HSIOM) registers” on page 39 • “System Resources Subsystem (SRSS) registers” on page 47 • “Timer, Counter, PWM (TCPWM) registers” on page 133
*E	2023-09-11	Updated “ROM Table registers” on page 320.
*F	2025-03-10	Updated hyperlinks: • PSOC™ 4000T MCU architecture reference manual on page 1 • PSOC™ 4 and PSOC 6™ MCU CAPSENSE™ design guide on page 256

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-03-10

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2025 Infineon Technologies AG.
All Rights Reserved.

Do you have a question about this document?

Email:

erratum@infineon.com

Document reference
002-34467 Rev. *F

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.