

# Programmable dual channel linear Hall sensor with fast SPC interface







#### **Features**

- Two highly accurate redundant Hall measurement channels (main and sub) integrated on one chip.
- Developed compliant to ISO 26262 (first edition 2011) Safety Element out of Context for safety requirements rated up to ASIL D.
- High diagnostic coverage by plausibility checking of main and sub signal on system level.
- Fast digital SPC interface with min.  $0.5\mu s$  unit time for transmission of main and sub signals in less than 500  $\mu s$ .
- Bus-capability for up to 4 sensor ICs on one data line.
- Selectable 12/14/16bit output signals, protected by CRC and rolling counter.
- Thin 4 pin leaded single sensor package.
- Operating automotive temperature range -40°C to 150°C.
- Digital temperature and stress compensation.
- Reverse-polarity and over voltage protection for VDD, GND and OUT pins.
- Main and sub channel programmable independently in EEPROM.
- Multipoint calibration up to 9 points.
- · Frameholder mechanism.
- Single-wire SICI programming interface on output pin.
- 2 x 16 bit user-configurable ID in EEPROM.

#### PRO-SIL™ Features

• Safety Manual and Safety Analysis Summary Report.

## **Potential applications**

- Robust replacement of potentiometers: No mechanical abrasion, resistant to humidity, temperature, pollution, and vibration.
- Linear and angular position sensing in automotive and industrial applications with highest accuracy requirements.
- Suited for safety applications such as pedal position, throttle position, and steering torque sensing.



## Programmable dual channel linear Hall sensor with fast SPC interface



## **Product validation**

Qualified for automotive applications. Product validation according to AEC-Q100.

## **Description**

The TLE4999C4 is a dual channel linear Hall sensor with a bus-capable digital Short-PWM-Code (SPC) interface. Both channels are integrated on one die in the chip.

The highly accurate measurement channels (main and sub) can be used for a plausibility check on system level. This enables a high diagnostic coverage.

The sensor is developed in compliance to **ISO 26262** (first edition 2011), supporting safety requirements on system level rated up to **ASIL D**.

Highest accuracy over a wide temperature range and lifetime is achieved by an integrated digital temperature- and stress-compensation.

**Table 1** Ordering Information

<b>Product Name</b>	Marking	Ordering Code	Package
TLE4999C4	4999C4	SP003420076	single sensor, PG-SSO-4-1

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Table of Contents**

	Features	. 1
	Potential applications	. 1
	Product validation	. 2
	Description	. 2
	Table of Contents	. :
1	Block diagram	
- 2	Pin and package configuration	
<b>3</b> 3.1	General     Functional description	
4	Application circuit	. 7
5	Maximum ratings	. 8
<b>6</b> 6.1	Operating range	
7	Electrical, magnetic and output parameters	10
8	SPC output	
8.1	SPC bus mode	
8.2	SPC unit times	15
8.3	SPC trigger pulse	15
8.4	Status nibble	
8.5	Short serial message	
8.6 8.7	Temperature nibbles	
8. <i>1</i> 8.8	Rolling Counter	
8.9	SPC frameholder	
9	Configuration and calibration parameters	
10	Package outlines	
10.1	Package marking	
	Terminology	23
11	Revision History	24



**Block diagram** 

## 1 Block diagram




Figure 1 Block diagram

## Programmable dual channel linear Hall sensor with fast SPC interface



Pin and package configuration

#### Pin and package configuration 2

Figure 2 shows the arrangement of the measurement channels of the TLE4999C4. The location of the Hall probes in the package and the pin configuration of the TLE4999C4 are shown in Figure 3.




Figure 2 **TLE4999C4 Package configuration** 

**TLE4999C4 Pin definitions and functions** Table 2

Pin No.	Symbol	TLE4999C4 Function
1	CBUF	Buffer capacitor pin <sup>1)</sup>
2	VDD	Supply voltage
3	GND	Ground
4	OUT	SPC output / programming interface I/O

<sup>1)</sup> In case CBUF capacitor is not used, CBUF pin shall be left floating




Figure 3 Pin Configuration of TLE4999C4 package

## Programmable dual channel linear Hall sensor with fast SPC interface



#### General

### 3 General

## 3.1 Functional description

The TLE4999C4 is a dual channel linear Hall sensor designed to meet the requirements of applications with highly accurate and reliable magnetic field measurement. The sensor provides a digital SPC (Short PWM Code) protocol on the OUT pin that is based on the SENT (Single Edge Nibble Transmission) standard. Configuration parameters can be programmed after assembly of the sensor in a module in an end-of-line calibration procedure using the serial inspection and configuration interface (SICI).

The two measurement channels have separate analog supply domains controlled by the main and sub analog regulators. These regulators feed separate biasing units for the main and sub Hall sensor elements.

A multiplexed second analog-digital converter (Sub HTS-ADC) is used to convert analog signals from the main and sub temperature sensors, and the sub Hall probe. The sub Hall, the temperature and the stress signals are fed into the second digital signal processing unit (DSP2).

The DSP2 uses the signals from all stress and temperature sensing elements for plausibility and range checks to ensure the integrity of the sensing elements and the analog signal path.

The analog signal of the main Hall probe is fed into an analog-digital converter (Main HADC), and is then processed in a digital signal processing unit (DSP1).

Each DSP uses its corresponding Hall signal, together with compensation parameters stored in the EEPROM, to calculate a Hall measurement value that is compensated for stress and temperature effects.

A high speed SPC protocol is generated containing the data of the two DSPs in the SPC protocol encoder and transmitted after a SPC trigger pulse.



**Application circuit** 

## 4 Application circuit

Figure 4 shows the recommended application circuit for two TLE4999C4 sensors.




Figure 4 Application circuit

Attention: The system integrator shall take in consideration that the maximum value of CL shall include also the capacitance of the bus line.

Note: For improved EMC capability the usage of a twisted cable is recommended.

## Programmable dual channel linear Hall sensor with fast SPC interface



**Maximum ratings** 

## 5 Maximum ratings

All specifications are valid over the full temperature range and over lifetime. They refer to each of the implemented sensors IC's, unless otherwise noted.

Table 3 Absolute maximum ratings

Parameter	Symbol	Limit \	<b>Limit Values</b>		Notes	
	Min. Max.					
Junction temperature	T <sub>J</sub>	-40	175	°C	max. 96h at 175°C <sup>1)</sup> (not additive)	
Non-operating temperature	T <sub>NO</sub>	-40	150	°C	max. 4400h (not additive) <sup>1)</sup>	
Maximum supply voltage	V <sub>DD</sub>	-20	20	V	max. 24 h for -40°C to 30°C T <sub>J</sub> max. 10 min. for 30°C to 80°C T <sub>J</sub> max. 30 s for 80°C to 125°C T <sub>J</sub> max. 15 s above 125°C T <sub>J</sub>	
Maximum voltage on OUT	V <sub>OUT</sub>	-18	19.5	V	max. 40 h (not additive)	
Maximum voltage on C <sub>Buf</sub>	V <sub>Cbuf</sub>	-0.3	20	V	max. 24 h for -40°C to 30°C T <sub>J</sub> max. 10 min. for 30°C to 80°C T <sub>J</sub> max. 30 s for 80°C to 125°C T <sub>J</sub> max. 15 s above 125°C T <sub>J</sub>	
Maximum voltage between 2 pins	V <sub>Diff</sub>	-20	20	V	max. 24 h for -40°C to 30°C T <sub>J</sub> max. 10 min. for 30°C to 80°C T <sub>J</sub> max. 30 s for 80°C to 125°C T <sub>J</sub> max. 15 s above 125°C T <sub>J</sub>	
Voltage peaks	$V_{DD}, V_{OUT}$	-	30	٧	for max. 50 μs	
OUT short circuit current <sup>2)</sup>	I <sub>OUT</sub>	-130	130	mA	max. 1 h	
Supply current in over voltage	I <sub>DD, ov</sub>		45	mA	time limitation for V <sub>DD</sub> applies	
Supply current in reverse voltage	I <sub>DD, rev</sub>	-75	-	mA	time limitation for V <sub>DD</sub> applies	
Magnetic flux density	B <sub>max</sub>	-	1000	mT		
ESD Immunity	$V_{HBM}$	-4	+4	kV	Human Body Model <sup>3)</sup>	
	V <sub>CDM</sub>	-0.75	+0.75	kV	Charged Device Model <sup>4)</sup>	

<sup>1)</sup> Maximum exposure time at other junction temperatures shall be calculated using the Arrhenius-model.

Note:

Any stress exceeding the values listed in **Table 3** may cause permanent damage to the device. The values given are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

<sup>2)</sup> Short to V<sub>DD</sub> or GND.

<sup>3)</sup> Human Body Model (HBM) according to ANSI/ESDA/JEDEC JS-001.

<sup>4)</sup> Charged Device Model (CDM) according to ANSI/ESDA/JEDEC JS-002.

## Programmable dual channel linear Hall sensor with fast SPC interface



**Operating range** 

## 6 Operating range

The following operating conditions shall not be exceeded in order to ensure correct operation of the TLE4999C4. All parameters specified in the following sections refer to these operating conditions.

Table 4 Operating range

Parameter	Symbol	ol Values			Unit	Notes	
		Min.	Тур.	Max.			
Supply voltage	$V_{DD}$	4.5	_	5.5	٧		
		V <sub>DD, pon</sub>	_	$V_{DD, poff}$	V	Extended range <sup>1)</sup>	
Supply voltage slew rate	V <sub>DD,slew</sub>	0.1	_	10 <sup>8</sup>	V/s	2)	
Operating junction temperature	T <sub>J</sub>	-40	-	165	°C	max. 1000h at 165°C <sup>3)</sup> (not additive)	
Output pull-up voltage	$V_{\text{pull-up}}$	3.0 <sup>4)</sup> /4.5	_	5.5	٧	5)6)	
Pull-up resistance	R <sub>P</sub>	1.45	2.2	10	kΩ	7)	
Load capacitance	$C_L$	1	_	3.9	nF	7)	
Supply capacitance	C <sub>s</sub>	_	100	_	nF		
Buffer capacitor	C <sub>Buf</sub>	_	68	_	nF		
Magnetic flux density	B	_	-	50	mT	Maximum measurement range	

- 1) No magnetic performance degradation in extended range between supply under voltage release level and supply over voltage release level.
- 2) The slew rate is the maximum voltage change per time and relates to the **Application circuit**.
- 3) Maximum exposure time at other junction temperatures shall be calculated using the Arrhenius-model.
- 4) Value valid only when the 3.3V bus capability bit is set in the EEPROM.
- 5) Output protocol characteristics depend on these parameters, RL must be according to max. output current. For the maximum output pull up voltage value refer to the note on **Table 3**.
- 6) The SPC output protocol will be deactivated when permanent voltages higher then 7.5V are present at the OUT pin.
- 7) Pull-up resistance and load capacitance have to be chosen in accordance with configured unit time, please see **Application circuit**.

### 6.1 Calculation of the junction temperature

The internal power dissipation  $P_{TOT}$  of the sensor increases the chip junction temperature above the ambient temperature (TA).

The power multiplied by the total thermal resistance **RthJA** (junction to ambient) added to TA leads to the final junction temperature. **RthJA** is the sum of the addition of the two components, Junction to Case and Case to Ambient.

$$\mathbf{RthJA} = \mathbf{R}_{\mathsf{thJC}} + \mathbf{R}_{\mathsf{thCA}}$$

TJ=TA +
$$\Delta$$
 T = R<sub>thJA</sub> xP<sub>TOT</sub> = R<sub>thJA</sub> x(V<sub>DD</sub> x I<sub>DD</sub> +V<sub>OUT</sub> x I<sub>OUT</sub>); I<sub>DD</sub>, I<sub>OUT</sub> > 0, if direction is into IC

Example (assuming no load on V<sub>OUT</sub>):

- VDD = 5.5 V
- IDD = 14.5mA
- Δ T= 165 [K/W] x (5.5 [V] x 0.0145 [A] + 0 [VA]) = 13.159K → 15K used for worst case scenario calculations

## Programmable dual channel linear Hall sensor with fast SPC interface



**Electrical, magnetic and output parameters** 

## 7 Electrical, magnetic and output parameters

All specifications are valid over the full temperature range and over lifetime. They refer to each of the implemented sensors IC's, if not otherwise noted.

Table 5 Electrical characteristics

Parameter	Symbol		Values	5	Unit	Notes	
		Min.	Тур.	Max.			
Supply current	I <sub>DD</sub>	4	_	14.5	mA		
Thermal resistance <sup>1)</sup>	R <sub>thJA</sub>	_	_	165	K/W	junction to ambient	
Power-on time <sup>2)</sup>	t <sub>pon</sub>	-	_	5	ms		
Supply under voltage reset/release level	V <sub>DD, pon</sub>	3.1	_	4.2	V		
Supply over voltage reset/release level	V <sub>DD, poff</sub>	6	-	7.5	V		
Supply voltage reset hysteresis	V <sub>DD,pon hyst</sub>	100	-	300	mV		
Out pin over voltage reset level	V <sub>OUT, ov res</sub>	7.5	8.25	9	V		
Out pin over voltage release level	V <sub>OUT, ov res</sub>	6	6.75	7.5	V		
Out pin over voltage reset hyteresis	V <sub>OUT, ov hyst</sub>	1	1.5	2	V		
Output saturation voltage	V <sub>OL</sub>	-	-	0.1*V <sub>DD</sub>	-	for I <sub>OUT</sub> ≤ 3.4mA	
Output fall and rise time	$t_{fall}/t_{rise}$	0.3	0.5	0.75	μs	for UT = 0.5 μs and 0.75 μs	
		0.6	1	1.4	μs	for UT = 1 μs and 1.25 μs	
		0.9	1.5	2.1	μs	for UT = 1.5 μs	
		1.2	2	2.8	μs	for UT = 2 μs and 2.5 μs	
		1.8	3	4.2	μs	for UT = 3 μs	
Output current	I <sub>OUT,avg</sub>			5	mA		
Output leakage current	I <sub>OUT Leak</sub>	20	100	120	μΑ	V <sub>pull-up</sub> = 5V and 0 < V <sub>DD</sub> < V <sub>DD, pon</sub>	
Oscillator frequency variation	Δf	-5	-	5	%	Nominal oscillator frequency: 20MHz	

<sup>1)</sup> Measured on 2s0p PCB board

The following **Figure 5** shows the operating area of the device, the condition for over voltage and under voltage and the corresponding sensor reaction. The values for the over- and under voltage comparators are the typical values from **Table 5**.

In the extended range, the sensor fulfills the full specification. However, voltages above the operating range can only be applied for a limited time (see **Table 3**).

<sup>2)</sup> Time since the sensor starts, until it is ready to respond to the first trigger pulse

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Electrical, magnetic and output parameters**




Figure 5 Operating area and sensor reaction for over- and under voltage.

Main and Sub channels of the TLE4999C4 provide highly accurate 12/14/16bit magnetic field signals. The output characteristics of the two channels are specified in **Table 6**.

Table 6 Magnetic and output characteristics of main and sub channel

Parameter	Symbol		Value	S	Unit	Notes
		Min.	Тур.	Max.		
Magnetic offset drift <sup>1)</sup>	$\Delta B_{OS\_Main}$	-100	_	100	μΤ	Main channel offset drift
	$\Delta B_{OS\_Sub}$	-200	_	200	μΤ	Sub channel offset drift
Magnetic initial offset	B <sub>OS</sub>	-300	_	300	μΤ	at 0h, 25 °C
Magnetic sensitivity drift <sup>1)</sup>	ΔS	-2.0	_	2.0	%	
Output noise (RMS) <sup>2)3)</sup>	OUT <sub>Noise_Main</sub>	-	-	0.6	LSB <sub>12</sub>	Main channel noise at 0h, 25 °C <sup>4)</sup>
	OUT <sub>Noise_Main</sub>	-	_	1	LSB <sub>12</sub>	Main channel noise <sup>1)</sup>
	OUT <sub>Noise_Sub</sub>	-	-	1.5	LSB <sub>12</sub>	Sub channel noise at 0h, 25 °C <sup>4)</sup>
	OUT <sub>Noise_Sub</sub>	-	_	2	LSB <sub>12</sub>	Sub channel noise <sup>1)</sup>
Magnetic hysteresis	B <sub>Hys</sub>	-	_	40	μΤ	
Integral non-linearity <sup>3)</sup>	INL	-4	_	4	LSB <sub>12</sub>	
Signal latency <sup>5)6)</sup>	t <sub>latency</sub>	-	-	200	μs	not including interface transmission time

<sup>1)</sup> Drift over temperature and lifetime

<sup>1)</sup> Value valid only when the 3.3V bus capability bit is set in the EEPROM.

<sup>2)</sup> For LP-Filter setting 8

<sup>3)</sup> Range 50 mT, gain 1.0 (scales linearly with gain)

<sup>4)</sup> Based on LSB16 calculation

<sup>5)</sup> Defined as phase shift of 100 Hz sine signal

<sup>6)</sup> For LP-Filter setting Off

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Electrical, magnetic and output parameters**

**Figure 6** shows the output characteristics of the sensor's main and sub channel in the default setting. The output characteristics can be changed by reconfiguring the zero point, gain and clamping ranges for main and sub channel (see **Chapter 9**).




Figure 6 Output characteristic

## Programmable dual channel linear Hall sensor with fast SPC interface



**SPC output** 

## 8 SPC output

The TLE4999C4 features a fast SPC (Short PWM Code) protocol, which is based on the SENT standard (Single Edge Nibble Transmission) defined by SAE J2716. As opposed to SENT, which implies a continuous transmission of data, the SPC protocol transmits data only after receiving a specific trigger pulse from the micro controller. The required length of the trigger pulse depends if the sensor is configured in synchronous mode or in bus mode. In case of bus mode the trigger pulse depends on the sensor number, which is configurable. Thereby, SPC allows the operation of up to four sensors on one bus line.

For the SPC interface the push pull setting with controlled slopes is used (the push-pull mode is only active during the slope controlled mode). In this configuration, the TLE4999C4 has controlled rising and falling slopes. Between the slope controlled transitions the HIGH level is maintained by the external pull-up resistor. Once the SPC protocol telegram is sent, the TLE4999C4 goes in to receiving mode (OUT Pin in Tri-sate mode) and waits until a valid trigger signal is received.




Figure 7 SPC default protocol example

As in the SENT protocol, the time between two consecutive falling edges defines the value of a 4-bit nibble, thus representing numbers between 0 and 15. The transmission time therefore depends on the transmitted data values. All values are multiples of a unit time frame (see **Table 8**). A SPC frame consists of the following nibbles (see **Table 7**):

- A trigger pulse by the master, which initiates the data transmission.
- A synchronization period of 56 UT.
- A status nibble of 12-27 UT, containing over voltage/error signaling and short serial message (SSM) data or the sensor ID.
- Between 3 and 4 data nibbles of 12-27 UT each (number is programmable), representing the Main Hall value
- Between 3 and 4 data nibbles of 12-27 UT each (number is programmable), representing the Sub Hall value.
- Optional 2 temperature nibbles of 12-27 UT each (programmable).
- Optional 2 /4 bit rolling counter of 12-27 UT (programmable).
- One or two checksum (CRC) nibbles of 12-27 UT each (programmable).
- An end pulse of 12 UT to terminate the SPC frame transmission.

The sensor is available for the next sample after the falling edge of the end pulse. The sensor's sampling time is at the beginning of the synchronization period, i.e. when a correct trigger is received.

## Programmable dual channel linear Hall sensor with fast SPC interface



## **SPC** output

Table 7 Frame selection

Frame Type	Parameter F	Data nibbles	Temperature nibbles	Rolling Counter	CRC bits
12 bit Main Hall, 12 Bit Sub Hall	A (default)	6 nibbles	_	_	4 bits
16 bit Main Hall, 16 Bit Sub Hall	В	8 nibbles	_	_	4 bits
12 bit Main Hall, 12 bit Sub Hall	С	6 nibbles	2 nibbles	_	4 bits
14 bit Main Hall, 14 bit Sub Hall	D	7 nibbles	_	2 x 2 bits <sup>1)</sup>	8 bits
12 bit Main Hall, 12 Bit Sub Hall	E	6 nibbles	_	2 bits <sup>2)</sup>	6 bits

- 1) Rolling counters combined with data nibbles, see Figure 8
- 2) Rolling counter combined with CRC nibble, see Figure 8




Figure 8 Content of the SPC protocol

#### 8.1 SPC bus mode

When the sensor is used in a bus mode with other sensors on a common SPC line, individual addresses have to be assigned to each sensor for identification. For the operation of the sensor in a SPC bus mode, it is strongly recommended that the sensor ID is written into the EEPROM of the sensor, as all sensors are pre configured with the default value "ID = 0" (see the *TLE4999C User Manual* for further details).

A corresponding trigger nibble from the micro controller can therefore address each sensor individually.

## Programmable dual channel linear Hall sensor with fast SPC interface



#### **SPC output**

The trigger nibble low time is shown in **Table 10**. Each low time corresponds to an individual sensor address. The total length of the trigger nibble can be selected to be constant at 90 UT (constant trigger length) or variable according to **Table 9**(variable trigger length).

#### 8.2 SPC unit times

Table 8 Programmable unit times

Parameter	Symbol	Values		Note or Test Condition
SPC unit time <sup>1)</sup>	UT	0.5, 0.75, 1.0, 1.25, 1.5, 2.0, 2.5, 3.0	μs	Clkunit=20MHz

<sup>1)</sup> Default setting is 3 μs nominal SPC unit time.

## 8.3 SPC trigger pulse

A SPC transmission is initiated by a trigger pulse from the ECU on the OUT pin. To detect a low-level on the OUT pin, the voltage has to be below the threshold  $V_{\text{th, falling}}$ . The sensor detects that the OUT line has been released as soon as  $V_{\text{th, rising}}$  is crossed. **Table 9** and **Figure 9** show the timing specification for the trigger pulse.

The master low time  $t_{\rm mlow}$  as well as the total trigger time  $t_{\rm mtr}$  are different for SPC bus mode on or off. With bus mode switched off, the total trigger time  $t_{\rm mtr}$  is shortest. This leads to a significantly shorter overall protocol transmission time for configurations where only one sensor IC is connected to the SPC line.

With bus mode switched on, it is possible to use up to four SPC sensors on one data line. The total trigger time in bus mode is longer, and can be selected between a constant trigger or a variable trigger.

The master low time  $t_{\text{mlow}}$  is used to identify the sensor ID of the addressed sensor IC, see **Table 10**. A proper addressing requires all sensors on the bus to be programmed with the same nominal SPC unit time.




Figure 9 SPC master pulse timing

Table 9 SPC master pulse parameters

Parameter	Symbol	Values			Unit	<b>Note or Test Condition</b>
		Min.	Тур.	Max.		
Falling edge threshold	$V_{thf}$	_	35	_	% of	1)2)
					$V_{DD}$	
Rising edge threshold	$V_{thr}$	_	50	_	% of	1)2)
					$V_{DD}$	

## Programmable dual channel linear Hall sensor with fast SPC interface



### **SPC output**

**Table 9 SPC master pulse parameters** (cont'd)

Parameter	Symbol		Values		Unit	Note or Test Condition
		Min.	Тур.	Max.		
Total trigger time	t <sub>mtr</sub>	_	13	-	UT	Bus mode off <sup>3)</sup>
		-	90	_	UT	Bus mode on, with constant trigger length <sup>3)</sup>
		-	t <sub>mlow,min</sub> + 12	-	UT	Bus mode on, with variable trigger length <sup>3)</sup>

- 1) Not subject to production test verified by design/characterization
- 2) Unit is % of nominal VDD (4.5V 5.5V)
- 3) Trigger time in the sensor is fixed to the number of unit times specified in the "typ." column, but the effective trigger time varies due to the sensor's oscillator variation

The below **Table 10** shows the trigger time window to which the sensor responds:

Table 10 Sensor SPC trigger parameters

Parameter	Symbol	Values			Unit	<b>Note or Test Condition</b>
		Min.	Тур.	Max.		
Master nibble low time	$t_{ m mlow}$	2	-	7	UT	Bus mode off <sup>1)</sup>
Master nibble low time	$t_{ m mlow}$	8	_	15	UT	Bus mode on, ID = 0
Master nibble low time	$t_{ m mlow}$	16	_	28	UT	Bus mode on, ID = 1
Master nibble low time	$t_{ m mlow}$	29	_	49	UT	Bus mode on, ID = 2
Master nibble low time	$t_{ m mlow}$	50	_	82	UT	Bus mode on, ID = 3

<sup>1)</sup> The combination of CL and pull-up resistor Rp may prevent use of some master nibble low times due to increased output rise time. Infineon recommends that for fast unit times (<=1.0us) the sensor is used in bus mode (with variable trigger option) with ID0 instead of bus mode off.

The below **Table 11** shows the trigger time window to be programmed in the ECU:

Table 11 ECU SPC trigger parameters

Parameter	Symbol	Values		Unit	Note or Test Condition	
		Min.	Тур.	Max.		
Master nibble low time	t <sub>mlow</sub>	2	_	4	UT	Bus mode off <sup>1)</sup>
Master nibble low time	$t_{ m mlow}$	9	_	12	UT	Bus mode on, ID = 0
Master nibble low time	$t_{ m mlow}$	19	-	23	UT	Bus mode on, ID = 1
Master nibble low time	$t_{ m mlow}$	35.5	_	40.5	UT	Bus mode on, ID = 2
Master nibble low time	$t_{ m mlow}$	61.5	-	67.5	UT	Bus mode on, ID = 3

<sup>1)</sup> The combination of CL and pull-up resistor Rp may prevent use of some master nibble low times due to increased output rise time. Infineon recommends that for fast unit times (<=1.0us) the sensor is used in bus mode (with variable trigger option) with ID0 instead of bus mode off.

Attention: For detailed description of the master nibble low times, please consult the application note for the TLE4999C, "Master nibble low time parameter and related tolerances".

#### Programmable dual channel linear Hall sensor with fast SPC interface



**SPC output** 

#### 8.4 Status nibble

The status nibble consists of 4 bits. The first two bits are status bits to monitor the internal status of the sensor whereas the last two bits can represent a short serial message (see **Chapter 8.5**) or the sensor ID. **Table 12** shows the usage of the status bits.

The status nibble, which is sent with each SPC data frame, provides an error indication. In case the sensor detects an error or an over voltage condition, the corresponding error bit in the status nibble is set. As long as the error or over voltage condition is present the error bit is set and the sensor output is disabled. After returning from the over voltage condition the corresponding error bit is set in the first transmitted frame in the status nibble.

Table 12 Structure of SPC status nibble

Bits	Description
[0] LSB	Short Serial Message bit (data) or bus mode ID LSB
[1]	Short Serial Message bit (start indication) or bus mode ID MSB
[2]	Return from over voltage condition/ internal error sub channel
[3] MSB	Startup/ internal error main channel

## 8.5 Short serial message

The short serial message is an additional option which can be enabled or disabled. The short serial message provides additional information in a slow channel transmitting an 8 bit temperature value of the main hall and 32 bit sensor ID (16 bits from main channel ID1 and 16 bits from sub channel ID2).

In each SPC frame, one bit of information is transmitted. The start of the short serial message is indicated by a "1" in bit [1] of the status nibble. For the next 15 SPC frames, this bit will contain a "0". The Information is transmitted in blocks of 16 bit with 1 bit per SPC frame in bit [0] of the status nibble.

4 bit message ID

8 bit data

4bit CRC (calculated from message ID and data bits)

The message ID is used for identification of the type of data received. All data are transmitted in the bit [0] of the status nibble in the order MSB to LSB.

The transmitted information is as follows:

Message -ID 0: 8 bit temperature value starting with MSB

Message -ID 1: 8 bit of sensor ID1 (starting with MSB)

Message -ID 2: 8 bit of sensor ID1 (starting with MSB-8)

Message -ID 3: 8 bit of sensor ID2 (starting with MSB)

Message -ID 4: 8 bit of sensor ID2 (starting with MSB-8)

Note: For further details please see the **TLE4999C User Manual.** 

## Programmable dual channel linear Hall sensor with fast SPC interface



**SPC output** 

## 8.6 Temperature nibbles

The temperature is coded as an 8 bit value. The value is transferred in unsigned integer format and corresponds to the range between -55 °C and +200 °C, so a transferred value of 55 corresponds to 0 °C. The temperature is additional information and although it is not calibrated, may be used for a plausibility check, for example. **Table 13** shows the mapping between junction temperature and the transmitted value in the SPC frame.

Table 13 Mapping of Temperature Value

Junction Temperature	Typ. Decimal Value from Sensor	Note
- 55 °C	0	Theoretical lower limit <sup>1)</sup>
0 °C	55	-
25 °C	80	-
200 °C	255	Theoretical upper limit <sup>1)</sup>

<sup>1)</sup> Theoretical range of temperature values, not operating temperature range.

## 8.7 Rolling Counter

The rolling counter is an additional option for a safety check implementation. Therefore the counter counts the number of transmitted frames with rollover back to 0 and increments with each message. The ECU can use this data for verification that no frame is missed or that no frame is sent repeatedly from the sensor.

There are two selectable protocols that include the rolling counter (see **Figure 8**), on frame D a 2 bit rolling counter is included in the first main data nibble and another 2 bit rolling counter in the first sub data nibble.

On frame E a 2 bit rolling counter is included in the CRC nibble, further details can be found in **Chapter 8.8**. There are frames without rolling counter bits, but to meet the safety requirements and target ASIL level of the application, it is recommended to use this function.

#### 8.8 CRC nibble

The CRC checksum can be used to check the validity of the decoded data. In the checksum included is the status nibble and the data nibbles. It is calculated using a polynomial  $(x^4 + x^3 + x^2 + 1)$  with a seed value of  $0101_B$ . The remainder after the last data nibble is transmitted as CRC.

To allow enhanced checksum for higher diagnostic coverage also 6 and 8 bit checksum are available to secure the data transmission (see **Table 7**).

The 6 bit checksum is calculated using a polynomial  $(x^6 + x + 1)$  with a seed value of  $010101_B$  and the 8 bit checksum is calculated using a polynomial  $(x^8 + x^5 + x^3 + x^2 + x + 1)$  with a seed value of  $01010101_B$ .

The calculation scheme of the CRC is described in detail in the TLE4999C User Manual.

#### 8.9 SPC frameholder

The frameholder functionality allows the user to operate multiple sensors in a bus configuration with synchronized sampling of the measurement value. This is achieved by having (apart from the SPC Bus ID) a separate frameholder ID for each chip on the bus which is used as a common signal trigger.

For further information please see TLE4999C User Manual.

## Programmable dual channel linear Hall sensor with fast SPC interface



**Configuration and calibration parameters** 

## 9 Configuration and calibration parameters

To perform the EEPROM programming with application and customer specific data the Serial Inspection and Configuration Interface (SICI) is used. The single wire interface uses the same pin as the SPC output for communication.

The TLE4999C4 has several configurable parameters which are stored in the EEPROM. These parameters affect the internal data processing and the output protocol. **Table 14** gives an overview of the magnetic measurement parameters, which can be configured separately for main and sub channel. **Table 15** shows the SPC interface parameters.

Table 14 TLE4999C4 Magnetic measurement parameters for main and sub Channel

Parameter	Setting range	Note
Magnetic range	±50 mT (default) ±25 mT	
Gain	-7.597.59	Gain value of $\pm 1.0$ corresponds to typical 36.875 LSB <sub>12</sub> /mT sensitivity in 50mT range, with $\pm 5\%$ clamping, (73.75 LSB <sub>12</sub> /mT in 25mT range, with $\pm 5\%$ clamping).
Zero point	0 LSB <sub>16</sub> 65535 LSB <sub>16</sub> <sup>1)</sup>	The user zero point setting is independently configurable for main and sub channels with 12, 14 or 16 bit granularity.  Default setting: 32768 LSB <sub>16</sub> .
Clamping low level	0 LSB <sub>16</sub> 65535 LSB <sub>16</sub> <sup>1)</sup>	Output clamping settings, see <b>Figure 6</b> .
Clamping high level	0 LSB <sub>16</sub> 65535 LSB <sub>16</sub> <sup>1)</sup>	Default setting: CL: 205 LSB <sub>16</sub> CH: 3890 LSB <sub>16</sub>
Multi point linearization	0 9 point	9 user selectable linearization points configurable in the EEPROM. The user can select the concentration either at the corners or around the middle point. For further details please see the
Low-pass filter <sup>2)</sup>	0: Off <sup>3)</sup> 1: 80Hz 2: 160 Hz 3: 200 Hz 4: 240 Hz 5: 320 Hz 6: 400 Hz 7: 470 Hz 8: 500 Hz (default) 9: 650 Hz 10: 870 Hz 11: 980 Hz 12: 1070 Hz 13: 1270 Hz 14: 1380 Hz 15: 1530 Hz	Low pass filter cut-off (-3 dB) frequency.

v01\_00

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Configuration and calibration parameters**

Table 14 TLE4999C4 Magnetic measurement parameters for main and sub Channel

Parameter	Setting range	Note
1 <sup>st</sup> order temperature coefficient TC <sub>1</sub> <sup>4)</sup>	-2400 ppm/°C 5400 ppm/°C	Second order user configurable temperature compensation.
2 <sup>nd</sup> order temperature coefficient TC <sub>2</sub> <sup>4)</sup>	-30 ppm/°C <sup>2</sup> 30 ppm/°C <sup>2</sup>	
Reference Temperature	0°C 127°C	
$T_0$		

<sup>1)</sup> The internal value is always 16 bit, in case the 12 or 14 bit setting range is used, the output will be clamped accordingly.

- 3) Set programmable low pass filter off, inherent filter of ADC stays on.
- 4) Adjusting the temperature coefficients (TC1 & TC2) can lead to a slight increase of the ADC noise level.

Table 15 TLE4999C4 SPC Interface parameters

Parameter	Setting range	Note
SPC protocol frames	2x 12 bit Hall + 4 bit CRC (default) 2x 16 bit Hall +4 bit CRC 2x 12 bit Hall + 8 bit temperature + 4 bit CRC 2x 14 bit Hall + 2x 2 bit RC + 8 bit CRC 2x 12 bit Hall + 2 bit RC + 6 bit CRC	see Table 7
SPC unit time <sup>1)</sup>	0.5 μs 3.0 μs	See chapter Chapter 8.2
SPC bus mode	On Off (default)	See chapter <b>Chapter 8.1</b>
SPC bus pull-up voltage	3.3V/5V	Default 5V
SPC ID	03	Default ID0
SPC variable trigger	On Off (default)	
SPC frameholder address <sup>2)</sup>	03	Default ID0

<sup>1)</sup> Subject to oscillator variation ±5%.


<sup>2)</sup> Subject to oscillator variation ±5%.

<sup>2)</sup> The SPC frameholder is deactivated in case the frameholder address is equal to the SPC address.



**Package outlines** 

#### **Package outlines** 10



PG-SSO (Plastic Green Single Small Outline), package dimensions

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Package outlines**

## 10.1 Package marking




Figure 11 PG-SSO (Plastic Green Single Small Outline), package marking

## **Green Product (RoHS compliant)**

To meet the world-wide customer requirements for environmentally friendly products, and to be compliant with government regulations the device is available as a green product. Green products are RoHS Compliant (i.e Pb free finish on leads and suitable for Pb free soldering according to IPC/JEDEC J-STD-020)

## Programmable dual channel linear Hall sensor with fast SPC interface



## **Terminology**

A

ADC Analog to digital converter

В

BIST Built-in self-test

C

CBUF Buffer capacitor

CRC Cyclic redundancy check

D

DSP Digital Signal Processing unit

Ε

ECC Error correction code to protect EEPROM content

EEPROM Electrically erasable and programmable read only memory - programmable memory for

(abbrev. EEP) sensor calibration and configuration data

G

GND Ground - ground line of sensor

Н

HADC Hall analog to digital converter

HTS-ADC Hall, temperature, stress analog to digital converter

ı

ID Identification

L

LP-Filter Low pass filter

LSB Least significant bit

М

MSB Most significant bit
MVS Margin voltage selector

0

OUT Digital output pin of the sensor

Ρ

PWM Pulse Width Modulation

R

RMS Root mean square ROM Read only memory

S

SICI Serial Inspection and Configuration Interface - Programming interface of the TLE4999C4

SPC Short PWM Code

T

TBD To be done

## Programmable dual channel linear Hall sensor with fast SPC interface



**Revision History** 

## 11 Revision History

Revision	Date	Changes
v01.00	2020-12-13	Initial release

#### Trademarks

Edition 2021-12-13 Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

#### IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.