

XMC7100 MCU registers

Technical reference manual

About this document

Scope and purpose

The XMC7100 registers TRM provides reference information for registers and contains respective programming details.

Intended audience

This manual is for system designer and programmers who are designing or programming using XMC 7100 parts.

Definitions

Register Permission

The following table lists the register permission based on protection context and privileges.

Permission	Description
READ	User mode = Read access, privilege mode = Read access, Non-secure = yes
PRIVILEGE - WRITE	User mode = Read access, privilege mode = Read and Write access, Non-secure = yes
NO-ACCESS	User mode = No access, Privilege mode = No access, Non-secure = yes
SECURE - READ	User mode = Read access, Privilege mode = Read access, Non-secure = No
FULL	Read and Write access in all modes, Non-secure = yes

Miscellaneous

Note: This device does not support LIN, SCB/LIN, and LPECO functionalities, any bit-field or description containing related feature is not applicable.

Software Access

The following table lists the behavior of registers, on various Software Read/Write Accesses.

SW Access	HW Access	Software Reads Register	Software Writes Register	Software Description
R	any	Register contents	Ignored	Software read-only
RW	any	Register contents	Register takes data written	Software read and write
RW1S	any	Register contents	Every bit is set upon writing 1	Software read and write 1 to set
RW0S	any	Register contents	Every bit is set upon writing 0	Software read and write 0 to set
RW1C	any	Register contents	Every bit is cleared upon writing 1	Software read and write 1 to clear
RW0C	any	Register contents	Every bit is cleared upon writing 0	Software read and write 0 to clear
RW1SC	any	NA	NA	Illegal
RW0SC	any	NA	NA	Illegal
W	any	Zero	Register takes data written	Software write only
W1S	any	Zero	Every bit is set upon writing 1	Software write 1 to set (no read)
W0S	any	Zero	Every bit is set upon writing 0	Software write 0 to set (no read)
W1C	any	Zero	Every bit is cleared upon writing 1	Software write 1 to clear (no read)
W0C	any	Zero	Every bit is cleared upon writing 0	Software write 0 to clear (no read)
W1SC	any	NA	NA	Illegal
W0SC	any	NA	NA	Illegal
A	any	NA	NA	Illegal

Hardware Access

The following table lists the behavior of registers, on various Hardware Read/Write Accesses.

HW Access	SW Access	Hardware Description
any	R	Hardware read only
any	RW	Hardware read and write
any	RW1S	Hardware read and set
any	RW0S	Hardware read and set
any	RW1C	Hardware read and clear
any	RW0C	Hardware read and clear
any	RW1SC	Hardware read and set/clear
any	RW0SC	Hardware read and set/clear
any	W	Write access only
any	W1S	Hardware set
any	W0S	Hardware set
any	W1C	Hardware clear
any	W0C	Hardware clear
any	W1SC	Hardware set/clear
any	W0SC	Hardware set/clear
R	A	Not supported
RW	A	Hardware read and write
RW1S	A	Hardware read and set
RW0S	A	Hardware read and set
RW1C	A	Hardware read and clear
RW0C	A	Hardware read and clear
RW1SC	A	Not supported
RW0SC	A	Not supported
W	A	Not supported
W1S	A	Not supported
W0S	A	Not supported
W1C	A	Not supported
W0C	A	Not supported
W1SC	A	Not supported
W0SC	A	Not supported

Core, Bus and Memory Access

The Cortex-M7 CPUSS uses AHB-Lite also for the system interconnect. Most of the IPs are compliant to the AHB-Lite protocol.

The AHB-Lite protocol is little endian; the least significant byte of a word is mapped onto the word's lowest byte address. IPs use a bus data width of 32 bit.

This allows for byte (8-bit), halfword (16-bit) and word (32-bit) transfers. We distinguish two types of transfer types:

- MMIO registers: These registers are typically used for IP control and status information. Unless otherwise noted, transfers to these registers must be 32-bit transfers; any other transfer size generates an AHB-Lite bus error. An IP's MMIO registers do not necessarily fully occupy a consecutive memory region; i.e. holes may be present in the region

- Memory structures: This includes generic memory structures, such as system FLASH, system RAM and system ROM, but also IP specific memory structures. Transfer to these memory structures may be 8-bit, 16-bit or 32-bit transfers; any other transfer size generates an AHB-Lite bus error. A memory structure fully occupies a consecutive memory region; i.e. no holes are present in the memory structure region

A bus slave memory region may contain both MMIO registers and zero or more memory structures. Gaps might exist in the bus slave's memory region, either due to gaps in the MMIO memory region or gaps between the MMIO and memory structure region(s)

Gaps in the address space are reserved. Do not access these gaps, if accessed can result in Hard faults or BUS ERROR depending on which bus segment or a peripheral an address space is allocated to.

List of Partnumber

This TRM is valid for the following part numbers.

MPN	Package	Code Flash(KB)	Work Flash(KB)	SRAM(KB)
XMC7100-F100K1088	100-TEQFP	1088	128	192
XMC7100-F100K2112	100-TEQFP	2112	128	384
XMC7100-F100K4160	100-TEQFP	4160	256	768
XMC7100D-F100K2112	100-TEQFP	2112	128	384
XMC7100D-F100K4160	100-TEQFP	4160	256	768
XMC7100-F144K2112	144-TEQFP	2112	128	384
XMC7100-F144K4160	144-TEQFP	4160	256	768
XMC7100D-F144K2112	144-TEQFP	2112	128	384
XMC7100D-F144K4160	144-TEQFP	4160	256	768
XMC7100-F176K4160	176-TEQFP	4160	256	768
XMC7100D-F176K4160	176-TEQFP	4160	256	768
XMC7100-E272K4160	272-BGA	4160	256	768
XMC7100D-E272K4160	272-BGA	4160	256	768

Memory mapping

MMIO	IP	Address	Description
MMIO0	PERI	0x40000000	Peripheral interconnect
	PERI_MS	0x40020000	Peripheral interconnect, master interface
	PERI_PCLK	0x40040000	Peripheral PCLK groups
MMIO1	CRYPTO	0x40100000	Cryptography component
MMIO2	CPUSS	0x40200000	CPU subsystem (CPUSS)
	FAULT	0x40210000	Fault structures
	IPC	0x40220000	IPC
	PROT	0x40230000	Protection
	FLASHC	0x40240000	Flash controller
	SRSS	0x40260000	SRSS Core Registers (ver3)
	BACKUP	0x40270000	SRSS Backup Domain (ver3)
	DW 0	0x40280000	Datawire Controller
	DW 1	0x40290000	Datawire Controller
	DMAC	0x402a0000	DMAC
	EFUSE	0x402c0000	EFUSE MXS40 registers
	EFUSE_DATA	0x402c0800	eFUSE memory
MMIO3	HSIOM	0x40300000	High Speed IO Matrix (HSIOM)
	GPIO	0x40310000	GPIO port control/configuration
	SMARTIO	0x40320000	Programmable IO configuration
	EVTGEN	0x403f0000	Event generator
MMIO4	SMIF	0x40420000	Serial Memory Interface
	SDHC	0x40460000	SD/eMMC Host Controller
	ETH	0x40480000	Ethernet Interface
MMIO5	CANFD 0	0x40520000	CAN Controller
	CANFD 1	0x40540000	CAN Controller
	TCPWM	0x40580000	Timer/Counter/PWM
MMIO6	SCB 0	0x40600000	Serial Communications Block (SPI/UART/I2C)
	SCB 1	0x40610000	Serial Communications Block (SPI/UART/I2C)
	SCB 2	0x40620000	Serial Communications Block (SPI/UART/I2C)
	SCB 3	0x40630000	Serial Communications Block (SPI/UART/I2C)
	SCB 4	0x40640000	Serial Communications Block (SPI/UART/I2C)
	SCB 5	0x40650000	Serial Communications Block (SPI/UART/I2C)
	SCB 6	0x40660000	Serial Communications Block (SPI/UART/I2C)
	SCB 7	0x40670000	Serial Communications Block (SPI/UART/I2C)
	SCB 8	0x40680000	Serial Communications Block (SPI/UART/I2C)
	SCB 9	0x40690000	Serial Communications Block (SPI/UART/I2C)
MMIO8	SCB 10	0x406a0000	Serial Communications Block (SPI/UART/I2C)
	I2S 0	0x40800000	I2S registers
	I2S 1	0x40801000	I2S registers
MMIO9	I2S 2	0x40802000	I2S registers
	PASS	0x40900000	Programmable Analog Subsystem for S40E
SFLASH	SFLASH	0x17000000	FLASH Supervisory Region
SYSTEM	CM0P	0xe0000000	Cortex-M0+ specific registers
	CM7	0xe0000000	Cortex-M7 specific registers
	SYSAP	0xe0000000	System debug Access Port (SYSAP) registers

1 BACKUP

Description SRSS Backup Domain (ver3)
Base Address 0x40270000
Size 0x10000
Slave Num MMIO2 - 6

Register Name	Address	Permission	Description
BACKUP_CTL	0x40270000	FULL	Control Note: VDDBAK_CTL VBACKUP_MEAS EN_CHARGE_KEY are not available for this register
BACKUP_RTC_RW	0x40270008	FULL	RTC Read Write register
BACKUP_CAL_CTL	0x4027000C	FULL	Oscillator calibration for absolute frequency
BACKUP_STATUS	0x40270010	FULL	Status
BACKUP_RTC_TIME	0x40270014	FULL	Calendar Seconds, Minutes, Hours, Day of Week
BACKUP_RTC_DATE	0x40270018	FULL	Calendar Day of Month, Month, Year
BACKUP_ALM1_TIME	0x4027001C	FULL	Alarm 1 Seconds, Minute, Hours, Day of Week
BACKUP_ALM1_DATE	0x40270020	FULL	Alarm 1 Day of Month, Month
BACKUP_ALM2_TIME	0x40270024	FULL	Alarm 2 Seconds, Minute, Hours, Day of Week
BACKUP_ALM2_DATE	0x40270028	FULL	Alarm 2 Day of Month, Month
BACKUP_INTR	0x4027002C	FULL	Interrupt request register
BACKUP_INTR_SET	0x40270030	FULL	Interrupt set request register
BACKUP_INTR_MASK	0x40270034	FULL	Interrupt mask register
BACKUP_INTR_MASKED	0x40270038	FULL	Interrupt masked request register
BACKUP_RESET	0x40270048	FULL	Backup reset register
BACKUP_BREG0	0x40271000	FULL	Backup register region
BACKUP_BREG1	0x40271004	FULL	Backup register region
BACKUP_BREG2	0x40271008	FULL	Backup register region
BACKUP_BREG3	0x4027100C	FULL	Backup register region

1.1 Register Details

1.1.1 BACKUP_CTL

Description: Control
Address: 0x40270000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				WCO_EN [3:3]	None [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		PRESCALER [13:12]		None [11:10]		CLK_SEL [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				VBACKUP_MEAS [19:19]	VDDBAK_CTL [18:17]		WCO_BYPASS [16:16]

Bits	31	30	29	28	27	26	25	24
Name	EN_CHARGE_KEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3	WCO_EN	RW	RW	0	Watch-crystal oscillator (WCO) enable. If there is a write in progress when this bit is cleared, the WCO will be internally kept on until the write completes. After enabling the WCO software must wait until STATUS.WCO_OK=1 before configuring any component that depends on clk_lf/clk_bak, like for example RTC or WDTs. Follow the procedure in BACKUP_RTC_RW to access this bit.
8:9	CLK_SEL	RW	RW	0	Clock select for RTC clock
	WCO			0	Watch-crystal oscillator input, available in Active, DeepSleep, Hibernate, and XRES.
	ALTBK			1	This allows to use the LFCLK selection as an alternate backup domain clock. Note that LFCLK is only available in Active and DeepSleep power modes. Note that LFCLK clock glitches can propagate into the backup logic when the clock is stopped. For this reason, if the WCO or ILO is intended as the clock source then choose it directly instead of routing through LFCLK.
	ILO			2	Internal Low frequency Oscillator, available in Active, DeepSleep, Hibernate, and XRES. For Hibernate operation CLK_ILO_CONFIG. ILO_BACKUP must be set. If there are multiple ILO, this is ILO0.
	LPECO_PRESCALER			3	Low-power external crystal oscillator prescaler output, available in Active, DeepSleep, Hibernate, and XRES.

Bits	Name	SW	HW	Default or Enum	Description
12:13	PRESCALER	RW	RW	0	Prescaler for real time clock used when WCO_BYPASS=1 and CLK_SEL = WCO. Configure this field before enabling the WCO, and do not change this setting when WCO_EN=1. 0: 32768 Hz square wave. Connect a 32768 Hz square wave to WCO output pin. Do not connect WCO input pin. 1: reserved 2: reserved 3: reserved
16	WCO_BYPASS	RW	RW	0	Configures the WCO for different board-level connections to the WCO pins. For example, this can be used to connect an external watch crystal oscillator instead of a watch crystal. In all cases, the two related GPIO pins (WCO input and output pins) must be configured as analog connections using GPIO registers, and they must be hooked at the board level as described below. Configure this field before enabling the WCO, and do not change this setting when WCO_EN=1. 0: Watch crystal. Connect a 32.768 kHz watch crystal between WCO input and output pins. 1: Clock signal, either a square wave or sine wave. See PRESCALER field for connection information.
17:18	VDDBAK_CTL	RW	RW	0	Controls the behavior of the switch that generates vddbak from vbackup or vddd. 0: automatically select vddd if its brownout detector says it is valid. If the brownout says its not valid, then use vmax which is the highest of vddd or vbackup. 1,2,3: force vddbak and vmax to select vbackup, regardless of its voltage.
19	VBACKUP_MEAS	RW	RW	0	Connect vbackup supply to the vbackup_meas output for measurement by an ADC attached to amuxbusa_adft_vddd. The vbackup_meas signal is scaled to 10 percent of vbackup, so it is within the supply range of the ADC.
24:31	EN_CHARGE_KEY	RW	RW	0	When set to 3C, the supercap charger circuit is enabled. Any other code disables the supercap charger. THIS CHARGING CIRCUIT IS FOR A SUPERCAP ONLY AND CANNOT SAFELY CHARGE A BATTERY. DO NOT WRITE THIS KEY WHEN VBACKUP IS CONNECTED TO A BATTERY.

1.1.2 BACKUP_RTC_RW

Description: RTC Read Write register
Address: 0x40270008
Offset: 0x8
Retention: Not Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain but reset in DEEPSLEEP.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						WRITE [1:1]	READ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	READ	RW	RW	0	Read bit When this bit is set the RTC registers will be copied to user registers and frozen so that a coherent RTC value can safely be read. The RTC will keep on running. Do not set the read bit if the RTC is still busy with a previous update (see RTC_BUSY bit) or if the Write bit is set. Do not set the Read bit at the same time that the Write bit is cleared.
1	WRITE	RW	RW	0	Write bit Only when this bit is set can the RTC registers be written to (otherwise writes are ignored). This bit cannot be set if the RTC is still busy with a previous update (see RTC_BUSY bit) or if the Read bit is set or getting set. The user writes to the RTC user registers, when the Write bit is cleared by the user then the user registers content is copied to the actual RTC registers. Only user RTC registers that were written to will get copied, others will not be affected. When the SECONDS field is updated then TICKS will also be reset (WDT is not affected). When the Write bit is cleared by a reset (brown out/DeepSleep) then the RTC update will be ignored/lost. Do not set the Write bit if the RTC if the RTC is still busy with a previous update (see RTC_BUSY). Do not set the Write bit at the same time that the Read bit is cleared.

1.1.3 BACKUP_CAL_CTL

Description: Oscillator calibration for absolute frequency
Address: 0x4027000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Calibration only works when the PRESCALER is set to 32768. Writes are ignored unless Write bit is set
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	CALIB_SIG N [6:6]	CALIB_VAL [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CAL_OUT [31:31]	None [30:30]	CAL_SEL [29:28]		None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	CALIB_VAL	RW	RW	0	Calibration value for absolute frequency (at a fixed temperature). Each step causes 128 ticks to be added or removed each hour. Effectively that means that each step is 1.085ppm (= 128/(60*60*32,768)). Positive values 0x01-0x3c (1..60) add pulses, negative values remove pulses, thus giving a range of +/-65.1 ppm (limited by 60 minutes per hour, not the range of this field) Calibration is performed hourly, starting at 59 minutes and 59 seconds, and applied as 64 ticks every 30 seconds until there have been 2*CALIB_VAL adjustments.
6	CALIB_SIGN	RW	RW	0	Calibration sign: 0= Negative sign: remove pulses (it takes more clock ticks to count one second) 1= Positive sign: add pulses (it takes less clock ticks to count one second)
28:29	CAL_SEL	RW	RW	0	Select calibration wave output signal
	CAL512			0	512Hz wave, not affected by calibration setting (not supported for 50/60Hz input clock: CTL.PRESCALER!=0)
	RESERVED			1	N/A
	CAL2			2	2Hz wave, includes the effect of the calibration setting, (not supported for 50/60Hz input clock: CTL.PRESCALER!=0)
	CAL1			3	1Hz wave, includes the effect of the calibration setting (supported for all input clocks)
31	CAL_OUT	RW	RW	0	Output enable for wave signal for calibration and allow CALIB_VAL to be written.

1.1.4 BACKUP_STATUS

Description: Status
Address: 0x40270010
Offset: 0x10
Retention: Not Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					WCO_OK [2:2]	None [1:1]	RTC_BUSY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RTC_BUSY	R	R	0	Pending RTC write
2	WCO_OK	R	R	0	Indicates that output has transitioned.

1.1.5 BACKUP_RTC_TIME

Description: Calendar Seconds, Minutes, Hours, Day of Week
Address: 0x40270014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RTC_SEC [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		RTC_MIN [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	CTRL_12HR [22:22]	None [21:21]	RTC_HOUR [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:27]					RTC_DAY [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	RTC_SEC	RW	RW	0	Calendar seconds, 0-59
8:13	RTC_MIN	RW	RW	0	Calendar minutes, 0-59
16:20	RTC_HOUR	RW	RW	0	Calendar hours, value depending on 12/24HR mode 0=24HR: [20:16]=0-23 1=12HR: [20]:0=AM, 1=PM, [19:16]=1-12
22	CTRL_12HR	RW	RW	0	Select 12/24HR mode: 1=12HR, 0=24HR
24:26	RTC_DAY	RW	RW	1	Calendar Day of the week, 1-7 It is up to the user to define the meaning of the values, but 1=Monday is recommended

1.1.6 BACKUP_RTC_DATE

Description: Calendar Day of Month, Month, Year
Address: 0x40270018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..
Default: 0x101

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			RTC_DATE [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				RTC_MON [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	RTC_YEAR [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	RTC_DATE	RW	RW	1	Calendar Day of the Month, 1-31 Automatic Leap Year Correction
8:11	RTC_MON	RW	RW	1	Calendar Month, 1-12
16:22	RTC_YEAR	RW	RW	0	Calendar year, 0-99

1.1.7 BACKUP_ALM1_TIME

Description: Alarm 1 Seconds, Minute, Hours, Day of Week
Address: 0x4027001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. This register is only used when BACKUP_ALM1_DATE.ALM_EN=1. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ALM_SEC_EN [7:7]	None [6:6]	ALM_SEC [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	ALM_MIN_EN [15:15]	None [14:14]	ALM_MIN [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	ALM_HOUR_EN [23:23]	None [22:21]		ALM_HOUR [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	ALM_DAY_EN [31:31]	None [30:27]				ALM_DAY [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	ALM_SEC	RW	RW	0	Alarm seconds, 0-59
7	ALM_SEC_EN	RW	RW	0	Alarm second enable: 0=ignore, 1=match
8:13	ALM_MIN	RW	RW	0	Alarm minutes, 0-59
15	ALM_MIN_EN	RW	RW	0	Alarm minutes enable: 0=ignore, 1=match
16:20	ALM_HOUR	RW	RW	0	Alarm hours, value depending on 12/24HR mode 24HR: [4:0]=0-23 12HR: [4]:0=AM, 1=PM, [3:0]=1-12
23	ALM_HOUR_EN	RW	RW	0	Alarm hour enable: 0=ignore, 1=match
24:26	ALM_DAY	RW	RW	1	Alarm Day of the week, 1-7 It is up to the user to define the meaning of the values, but 1=Monday is recommended
31	ALM_DAY_EN	RW	RW	0	Alarm Day of the Week enable: 0=ignore, 1=match

1.1.8 BACKUP_ALM1_DATE

Description: Alarm 1 Day of Month, Month

Address: 0x40270020

Offset: 0x20

Retention: Retained

IsDeepSleep: No

Comment: These bits are in vddbak domain. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..

Default: 0x101

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ALM_DATE_EN [7:7]	None [6:5]		ALM_DATE [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	ALM_MON_EN [15:15]	None [14:12]			ALM_MON [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ALM_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	ALM_DATE	RW	RW	1	Alarm Day of the Month, 1-31 Leap Year corrected
7	ALM_DATE_EN	RW	RW	0	Alarm Day of the Month enable: 0=ignore, 1=match
8:11	ALM_MON	RW	RW	1	Alarm Month, 1-12
15	ALM_MON_EN	RW	RW	0	Alarm Month enable: 0=ignore, 1=match
31	ALM_EN	RW	RW	0	Master enable for alarm 1. 0: Alarm 1 is disabled. Fields for date and time are ignored. 1: Alarm 1 is enabled. Alarm triggers whenever the new date and time matches all the enabled date and time fields, which can happen more than once depending on configuration. If none of the date and time fields are enabled, then this alarm triggers once every second.

1.1.9 BACKUP_ALM2_TIME

Description: Alarm 2 Seconds, Minute, Hours, Day of Week
Address: 0x40270024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. This register is only used when BACKUP_ALM2_DATE.ALM_EN=1. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ALM_SEC_EN [7:7]	None [6:6]	ALM_SEC [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	ALM_MIN_EN [15:15]	None [14:14]	ALM_MIN [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	ALM_HOUR_EN [23:23]	None [22:21]		ALM_HOUR [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	ALM_DAY_EN [31:31]	None [30:27]				ALM_DAY [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	ALM_SEC	RW	RW	0	Alarm seconds, 0-59
7	ALM_SEC_EN	RW	RW	0	Alarm second enable: 0=ignore, 1=match
8:13	ALM_MIN	RW	RW	0	Alarm minutes, 0-59
15	ALM_MIN_EN	RW	RW	0	Alarm minutes enable: 0=ignore, 1=match
16:20	ALM_HOUR	RW	RW	0	Alarm hours, value depending on 12/24HR mode 24HR: [4:0]=0-23 12HR: [4]:0=AM, 1=PM, [3:0]=1-12
23	ALM_HOUR_EN	RW	RW	0	Alarm hour enable: 0=ignore, 1=match
24:26	ALM_DAY	RW	RW	1	Alarm Day of the week, 1-7 It is up to the user to define the meaning of the values, but 1=Monday is recommended
31	ALM_DAY_EN	RW	RW	0	Alarm Day of the Week enable: 0=ignore, 1=match

1.1.10 BACKUP_ALM2_DATE

Description: Alarm 2 Day of Month, Month

Address: 0x40270028

Offset: 0x28

Retention: Retained

IsDeepSleep: No

Comment: These bits are in vddbak domain. Writes are ignored unless Write bit is set. After reset, these will read as zero until the read bit is set and the values are copied from the RTC into these registers..

Default: 0x101

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ALM_DATE_EN [7:7]	None [6:5]		ALM_DATE [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	ALM_MON_EN [15:15]	None [14:12]			ALM_MON [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ALM_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	ALM_DATE	RW	RW	1	Alarm Day of the Month, 1-31 Leap Year corrected
7	ALM_DATE_EN	RW	RW	0	Alarm Day of the Month enable: 0=ignore, 1=match
8:11	ALM_MON	RW	RW	1	Alarm Month, 1-12
15	ALM_MON_EN	RW	RW	0	Alarm Month enable: 0=ignore, 1=match
31	ALM_EN	RW	RW	0	Master enable for alarm 2. 0: Alarm 2 is disabled. Fields for date and time are ignored. 1: Alarm 2 is enabled. Alarm triggers whenever the new date and time matches all the enabled date and time fields, which can happen more than once depending on configuration. If none of the date and time fields are enabled, then this alarm triggers once every second.

1.1.11 BACKUP_INTR

Description: Interrupt request register
Address: 0x4027002C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Interrupt signal from SRSS includes this register and also BACKUP_INTR, if present.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CENTURY [2:2]	ALARM2 [1:1]	ALARM1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALARM1	RW1C	RW1C	0	Alarm 1 Interrupt
1	ALARM2	RW1C	RW1C	0	Alarm 2 Interrupt
2	CENTURY	RW1C	RW1C	0	Century overflow interrupt

1.1.12 BACKUP_INTR_SET

Description: Interrupt set request register
Address: 0x40270030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Allows setting interrupts for firmware testing.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CENTURY [2:2]	ALARM2 [1:1]	ALARM1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALARM1	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	ALARM2	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	CENTURY	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

1.1.13 BACKUP_INTR_MASK

Description: Interrupt mask register
Address: 0x40270034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. When Mask bit is set the interrupt is enabled.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CENTURY [2:2]	ALARM2 [1:1]	ALARM1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALARM1	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	ALARM2	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	CENTURY	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

1.1.14 BACKUP_INTR_MASKED

Description: Interrupt masked request register

Address: 0x40270038

Offset: 0x38

Retention: Retained

IsDeepSleep: No

Comment: These bits are in vddbak domain. When read, this register reflects a bitwise and between the interrupt request and mask registers.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CENTURY [2:2]	ALARM2 [1:1]	ALARM1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALARM1	R	R	0	Logical and of corresponding request and mask bits.
1	ALARM2	R	R	0	Logical and of corresponding request and mask bits.
2	CENTURY	R	R	0	Logical and of corresponding request and mask bits.

1.1.15 BACKUP_RESET

Description: Backup reset register
Address: 0x40270048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: This register is used to reset the backup domain from firmware.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESET [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	RESET	RW1S	RW1S	0	Writing 1 to this register resets the backup logic. Hardware clears it when the reset is complete. After setting this register, firmware should confirm it reads as 0 before attempting to write other backup registers.

1.1.16 BACKUP_BREG

Description: Backup register region
Address: 0x40271000
Offset: 0x1000
Retention: Retained
IsDeepSleep: No
Comment: These bits are in vddbak domain. Backup memory
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BREG [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	BREG [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BREG [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BREG [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	BREG	RW	RW	0	Backup memory that contains application-specific data. Memory is retained on vbackup supply.

2 CANFD

2.1 CANFD 0

Description	CAN Controller
Base Address	0x40520000
Size	0x20000
Slave Num	MMIO5 - 1

Register Name	Address	Permission	Description
CANFD0_CTL	0x40521000	FULL	Global CAN control register
CANFD0_STATUS	0x40521004	FULL	Global CAN status register
CANFD0_INTR0_CAUSE	0x40521010	FULL	Consolidated interrupt0 cause register
CANFD0_INTR1_CAUSE	0x40521014	FULL	Consolidated interrupt1 cause register
CANFD0_TS_CTL	0x40521020	FULL	Time Stamp control register
CANFD0_TS_CNT	0x40521024	FULL	Time Stamp counter value
CANFD0_ECC_CTL	0x40521080	FULL	ECC control
CANFD0_ECC_ERR_INJ	0x40521084	FULL	ECC error injection

2.1.1 CH 0

Register Name	Address	Permission	Description
CANFD0_CH0_RXFTOP_CTL	0x40520180	FULL	Receive FIFO Top control
CANFD0_CH0_RXFTOP0_STAT	0x405201A0	FULL	Receive FIFO 0 Top Status
CANFD0_CH0_RXFTOP0_DATA	0x405201A8	FULL	Receive FIFO 0 Top Data
CANFD0_CH0_RXFTOP1_STAT	0x405201B0	FULL	Receive FIFO 1 Top Status
CANFD0_CH0_RXFTOP1_DATA	0x405201B8	FULL	Receive FIFO 1 Top Data

2.1.1.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD0_CH0_CREL	0x40520000	FULL	Core Release Register
CANFD0_CH0_ENDN	0x40520004	FULL	Endian Register
CANFD0_CH0_DBTP	0x4052000C	FULL	Data Bit Timing & Prescaler Register
CANFD0_CH0_TEST	0x40520010	FULL	Test Register
CANFD0_CH0_RWD	0x40520014	FULL	RAM Watchdog
CANFD0_CH0_CCCR	0x40520018	FULL	CC Control Register
CANFD0_CH0_NBTP	0x4052001C	FULL	Nominal Bit Timing & Prescaler Register
CANFD0_CH0_TSCC	0x40520020	FULL	Timestamp Counter Configuration
CANFD0_CH0_TSCV	0x40520024	FULL	Timestamp Counter Value
CANFD0_CH0_TOCC	0x40520028	FULL	Timeout Counter Configuration
CANFD0_CH0_TOCV	0x4052002C	FULL	Timeout Counter Value
CANFD0_CH0_ECR	0x40520040	FULL	Error Counter Register
CANFD0_CH0_PSR	0x40520044	FULL	Protocol Status Register
CANFD0_CH0_TDCR	0x40520048	FULL	Transmitter Delay Compensation Register
CANFD0_CH0_IR	0x40520050	FULL	Interrupt Register
CANFD0_CH0_IE	0x40520054	FULL	Interrupt Enable
CANFD0_CH0_ILS	0x40520058	FULL	Interrupt Line Select
CANFD0_CH0_ILE	0x4052005C	FULL	Interrupt Line Enable
CANFD0_CH0_GFC	0x40520080	FULL	Global Filter Configuration
CANFD0_CH0_SIDFC	0x40520084	FULL	Standard ID Filter Configuration
CANFD0_CH0_XIDFC	0x40520088	FULL	Extended ID Filter Configuration
CANFD0_CH0_XIDAM	0x40520090	FULL	Extended ID AND Mask
CANFD0_CH0_HPMS	0x40520094	FULL	High Priority Message Status
CANFD0_CH0_NDAT1	0x40520098	FULL	New Data 1
CANFD0_CH0_NDAT2	0x4052009C	FULL	New Data 2
CANFD0_CH0_RXF0C	0x405200A0	FULL	Rx FIFO 0 Configuration
CANFD0_CH0_RXF0S	0x405200A4	FULL	Rx FIFO 0 Status
CANFD0_CH0_RXF0A	0x405200A8	FULL	Rx FIFO 0 Acknowledge
CANFD0_CH0_RXBC	0x405200AC	FULL	Rx Buffer Configuration
CANFD0_CH0_RXF1C	0x405200B0	FULL	Rx FIFO 1 Configuration
CANFD0_CH0_RXF1S	0x405200B4	FULL	Rx FIFO 1 Status
CANFD0_CH0_RXF1A	0x405200B8	FULL	Rx FIFO 1 Acknowledge
CANFD0_CH0_RXESC	0x405200BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD0_CH0_TXBC	0x405200C0	FULL	Tx Buffer Configuration

Register Name	Address	Permission	Description
CANFD0_CH0_TXFQS	0x405200C4	FULL	Tx FIFO/Queue Status
CANFD0_CH0_TXESC	0x405200C8	FULL	Tx Buffer Element Size Configuration
CANFD0_CH0_TXBRP	0x405200CC	FULL	Tx Buffer Request Pending
CANFD0_CH0_TXBAR	0x405200D0	FULL	Tx Buffer Add Request
CANFD0_CH0_TXBCR	0x405200D4	FULL	Tx Buffer Cancellation Request
CANFD0_CH0_TXBTO	0x405200D8	FULL	Tx Buffer Transmission Occurred
CANFD0_CH0_TXBCF	0x405200DC	FULL	Tx Buffer Cancellation Finished
CANFD0_CH0_TXBTIE	0x405200E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD0_CH0_TXBCIE	0x405200E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD0_CH0_TXEFC	0x405200F0	FULL	Tx Event FIFO Configuration
CANFD0_CH0_TXEFS	0x405200F4	FULL	Tx Event FIFO Status
CANFD0_CH0_TXEFA	0x405200F8	FULL	Tx Event FIFO Acknowledge
CANFD0_CH0_TTMC	0x40520100	FULL	TT Trigger Memory Configuration
CANFD0_CH0_TTRMC	0x40520104	FULL	TT Reference Message Configuration
CANFD0_CH0_TTOCF	0x40520108	FULL	TT Operation Configuration
CANFD0_CH0_TTMLM	0x4052010C	FULL	TT Matrix Limits
CANFD0_CH0_TURCF	0x40520110	FULL	TUR Configuration
CANFD0_CH0_TTOCN	0x40520114	FULL	TT Operation Control
CANFD0_CH0_TTGP	0x40520118	FULL	TT Global Time Preset
CANFD0_CH0_TTTMK	0x4052011C	FULL	TT Time Mark
CANFD0_CH0_TTIR	0x40520120	FULL	TT Interrupt Register
CANFD0_CH0_TTIE	0x40520124	FULL	TT Interrupt Enable
CANFD0_CH0_TTILS	0x40520128	FULL	TT Interrupt Line Select
CANFD0_CH0_TTOST	0x4052012C	FULL	TT Operation Status
CANFD0_CH0_TURNA	0x40520130	FULL	TUR Numerator Actual
CANFD0_CH0_TTLGT	0x40520134	FULL	TT Local & Global Time
CANFD0_CH0_TTCTC	0x40520138	FULL	TT Cycle Time & Count
CANFD0_CH0_TTCPT	0x4052013C	FULL	TT Capture Time
CANFD0_CH0_TTCSM	0x40520140	FULL	TT Cycle Sync Mark

2.1.2 CH 1

Register Name	Address	Permission	Description
CANFD0_CH1_RXFTOP_CTL	0x40520380	FULL	Receive FIFO Top control
CANFD0_CH1_RXFTOP0_STAT	0x405203A0	FULL	Receive FIFO 0 Top Status
CANFD0_CH1_RXFTOP0_DATA	0x405203A8	FULL	Receive FIFO 0 Top Data
CANFD0_CH1_RXFTOP1_STAT	0x405203B0	FULL	Receive FIFO 1 Top Status
CANFD0_CH1_RXFTOP1_DATA	0x405203B8	FULL	Receive FIFO 1 Top Data

2.1.2.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD0_CH1_CREL	0x40520200	FULL	Core Release Register
CANFD0_CH1_ENDN	0x40520204	FULL	Endian Register
CANFD0_CH1_DBTP	0x4052020C	FULL	Data Bit Timing & Prescaler Register
CANFD0_CH1_TEST	0x40520210	FULL	Test Register
CANFD0_CH1_RWD	0x40520214	FULL	RAM Watchdog
CANFD0_CH1_CCCR	0x40520218	FULL	CC Control Register
CANFD0_CH1_NBTP	0x4052021C	FULL	Nominal Bit Timing & Prescaler Register
CANFD0_CH1_TSCC	0x40520220	FULL	Timestamp Counter Configuration
CANFD0_CH1_TSCV	0x40520224	FULL	Timestamp Counter Value
CANFD0_CH1_TOCC	0x40520228	FULL	Timeout Counter Configuration
CANFD0_CH1_TOCV	0x4052022C	FULL	Timeout Counter Value
CANFD0_CH1_ECR	0x40520240	FULL	Error Counter Register
CANFD0_CH1_PSR	0x40520244	FULL	Protocol Status Register
CANFD0_CH1_TDCR	0x40520248	FULL	Transmitter Delay Compensation Register
CANFD0_CH1_IR	0x40520250	FULL	Interrupt Register
CANFD0_CH1_IE	0x40520254	FULL	Interrupt Enable
CANFD0_CH1_ILS	0x40520258	FULL	Interrupt Line Select
CANFD0_CH1_ILE	0x4052025C	FULL	Interrupt Line Enable
CANFD0_CH1_GFC	0x40520280	FULL	Global Filter Configuration
CANFD0_CH1_SIDFC	0x40520284	FULL	Standard ID Filter Configuration
CANFD0_CH1_XIDFC	0x40520288	FULL	Extended ID Filter Configuration
CANFD0_CH1_XIDAM	0x40520290	FULL	Extended ID AND Mask
CANFD0_CH1_HPMS	0x40520294	FULL	High Priority Message Status

Register Name	Address	Permission	Description
CANFD0_CH1_NDAT1	0x40520298	FULL	New Data 1
CANFD0_CH1_NDAT2	0x4052029C	FULL	New Data 2
CANFD0_CH1_RXF0C	0x405202A0	FULL	Rx FIFO 0 Configuration
CANFD0_CH1_RXF0S	0x405202A4	FULL	Rx FIFO 0 Status
CANFD0_CH1_RXF0A	0x405202A8	FULL	Rx FIFO 0 Acknowledge
CANFD0_CH1_RXBC	0x405202AC	FULL	Rx Buffer Configuration
CANFD0_CH1_RXF1C	0x405202B0	FULL	Rx FIFO 1 Configuration
CANFD0_CH1_RXF1S	0x405202B4	FULL	Rx FIFO 1 Status
CANFD0_CH1_RXF1A	0x405202B8	FULL	Rx FIFO 1 Acknowledge
CANFD0_CH1_RXESC	0x405202BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD0_CH1_TXBC	0x405202C0	FULL	Tx Buffer Configuration
CANFD0_CH1_TXFQS	0x405202C4	FULL	Tx FIFO/Queue Status
CANFD0_CH1_TXESC	0x405202C8	FULL	Tx Buffer Element Size Configuration
CANFD0_CH1_TXBRP	0x405202CC	FULL	Tx Buffer Request Pending
CANFD0_CH1_TXBAR	0x405202D0	FULL	Tx Buffer Add Request
CANFD0_CH1_TXBCR	0x405202D4	FULL	Tx Buffer Cancellation Request
CANFD0_CH1_TXBTO	0x405202D8	FULL	Tx Buffer Transmission Occurred
CANFD0_CH1_TXBCF	0x405202DC	FULL	Tx Buffer Cancellation Finished
CANFD0_CH1_TXBTIE	0x405202E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD0_CH1_TXBCIE	0x405202E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD0_CH1_TXEFC	0x405202F0	FULL	Tx Event FIFO Configuration
CANFD0_CH1_TXEFS	0x405202F4	FULL	Tx Event FIFO Status
CANFD0_CH1_TXEFA	0x405202F8	FULL	Tx Event FIFO Acknowledge
CANFD0_CH1_TTTMC	0x40520300	FULL	TT Trigger Memory Configuration
CANFD0_CH1_TTRMC	0x40520304	FULL	TT Reference Message Configuration
CANFD0_CH1_TTOCF	0x40520308	FULL	TT Operation Configuration
CANFD0_CH1_TTMLM	0x4052030C	FULL	TT Matrix Limits
CANFD0_CH1_TURCF	0x40520310	FULL	TUR Configuration
CANFD0_CH1_TTOCN	0x40520314	FULL	TT Operation Control
CANFD0_CH1_TTGRP	0x40520318	FULL	TT Global Time Preset
CANFD0_CH1_TTTMK	0x4052031C	FULL	TT Time Mark
CANFD0_CH1_TTIR	0x40520320	FULL	TT Interrupt Register
CANFD0_CH1_TTIE	0x40520324	FULL	TT Interrupt Enable
CANFD0_CH1_TTILS	0x40520328	FULL	TT Interrupt Line Select
CANFD0_CH1_TTOST	0x4052032C	FULL	TT Operation Status
CANFD0_CH1_TURNA	0x40520330	FULL	TUR Numerator Actual
CANFD0_CH1_TLGT	0x40520334	FULL	TT Local & Global Time
CANFD0_CH1_TTCTC	0x40520338	FULL	TT Cycle Time & Count
CANFD0_CH1_TTCPT	0x4052033C	FULL	TT Capture Time
CANFD0_CH1_TTCSM	0x40520340	FULL	TT Cycle Sync Mark

2.1.3 CH 2

Register Name	Address	Permission	Description
CANFD0_CH2_RXFTOP_CTL	0x40520580	FULL	Receive FIFO Top control
CANFD0_CH2_RXFTOP0_STAT	0x405205A0	FULL	Receive FIFO 0 Top Status
CANFD0_CH2_RXFTOP0_DATA	0x405205A8	FULL	Receive FIFO 0 Top Data
CANFD0_CH2_RXFTOP1_STAT	0x405205B0	FULL	Receive FIFO 1 Top Status
CANFD0_CH2_RXFTOP1_DATA	0x405205B8	FULL	Receive FIFO 1 Top Data

2.1.3.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD0_CH2_CREL	0x40520400	FULL	Core Release Register
CANFD0_CH2_ENDN	0x40520404	FULL	Endian Register
CANFD0_CH2_DBTP	0x4052040C	FULL	Data Bit Timing & Prescaler Register
CANFD0_CH2_TEST	0x40520410	FULL	Test Register
CANFD0_CH2_RWD	0x40520414	FULL	RAM Watchdog
CANFD0_CH2_CCCR	0x40520418	FULL	CC Control Register
CANFD0_CH2_NBTP	0x4052041C	FULL	Nominal Bit Timing & Prescaler Register
CANFD0_CH2_TSCC	0x40520420	FULL	Timestamp Counter Configuration
CANFD0_CH2_TSCV	0x40520424	FULL	Timestamp Counter Value
CANFD0_CH2_TOCC	0x40520428	FULL	Timeout Counter Configuration
CANFD0_CH2_TOCV	0x4052042C	FULL	Timeout Counter Value
CANFD0_CH2_ECR	0x40520440	FULL	Error Counter Register

Register Name	Address	Permission	Description
CANFD0_CH2_PSR	0x40520444	FULL	Protocol Status Register
CANFD0_CH2_TDCR	0x40520448	FULL	Transmitter Delay Compensation Register
CANFD0_CH2_IR	0x40520450	FULL	Interrupt Register
CANFD0_CH2_IE	0x40520454	FULL	Interrupt Enable
CANFD0_CH2_ILS	0x40520458	FULL	Interrupt Line Select
CANFD0_CH2_ILE	0x4052045C	FULL	Interrupt Line Enable
CANFD0_CH2_GFC	0x40520480	FULL	Global Filter Configuration
CANFD0_CH2_SIDFC	0x40520484	FULL	Standard ID Filter Configuration
CANFD0_CH2_XIDFC	0x40520488	FULL	Extended ID Filter Configuration
CANFD0_CH2_XIDAM	0x40520490	FULL	Extended ID AND Mask
CANFD0_CH2_HPMS	0x40520494	FULL	High Priority Message Status
CANFD0_CH2_NDAT1	0x40520498	FULL	New Data 1
CANFD0_CH2_NDAT2	0x4052049C	FULL	New Data 2
CANFD0_CH2_RXF0C	0x405204A0	FULL	Rx FIFO 0 Configuration
CANFD0_CH2_RXF0S	0x405204A4	FULL	Rx FIFO 0 Status
CANFD0_CH2_RXF0A	0x405204A8	FULL	Rx FIFO 0 Acknowledge
CANFD0_CH2_RXBC	0x405204AC	FULL	Rx Buffer Configuration
CANFD0_CH2_RXF1C	0x405204B0	FULL	Rx FIFO 1 Configuration
CANFD0_CH2_RXF1S	0x405204B4	FULL	Rx FIFO 1 Status
CANFD0_CH2_RXF1A	0x405204B8	FULL	Rx FIFO 1 Acknowledge
CANFD0_CH2_RXESC	0x405204BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD0_CH2_TXBC	0x405204C0	FULL	Tx Buffer Configuration
CANFD0_CH2_TXFQS	0x405204C4	FULL	Tx FIFO/Queue Status
CANFD0_CH2_TXESC	0x405204C8	FULL	Tx Buffer Element Size Configuration
CANFD0_CH2_TXBRP	0x405204CC	FULL	Tx Buffer Request Pending
CANFD0_CH2_TXBAR	0x405204D0	FULL	Tx Buffer Add Request
CANFD0_CH2_TXBCR	0x405204D4	FULL	Tx Buffer Cancellation Request
CANFD0_CH2_TXBTO	0x405204D8	FULL	Tx Buffer Transmission Occurred
CANFD0_CH2_TXBCF	0x405204DC	FULL	Tx Buffer Cancellation Finished
CANFD0_CH2_TXBTIE	0x405204E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD0_CH2_TXBCIE	0x405204E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD0_CH2_TXEFC	0x405204F0	FULL	Tx Event FIFO Configuration
CANFD0_CH2_TXEFS	0x405204F4	FULL	Tx Event FIFO Status
CANFD0_CH2_TXEFA	0x405204F8	FULL	Tx Event FIFO Acknowledge
CANFD0_CH2_TTTMC	0x40520500	FULL	TT Trigger Memory Configuration
CANFD0_CH2_TTRMC	0x40520504	FULL	TT Reference Message Configuration
CANFD0_CH2_TTOCF	0x40520508	FULL	TT Operation Configuration
CANFD0_CH2_TTMLM	0x4052050C	FULL	TT Matrix Limits
CANFD0_CH2_TURCF	0x40520510	FULL	TUR Configuration
CANFD0_CH2_TTOCN	0x40520514	FULL	TT Operation Control
CANFD0_CH2_TTGPL	0x40520518	FULL	TT Global Time Preset
CANFD0_CH2_TTTMK	0x4052051C	FULL	TT Time Mark
CANFD0_CH2_TTIR	0x40520520	FULL	TT Interrupt Register
CANFD0_CH2_TTIE	0x40520524	FULL	TT Interrupt Enable
CANFD0_CH2_TTILS	0x40520528	FULL	TT Interrupt Line Select
CANFD0_CH2_TTOST	0x4052052C	FULL	TT Operation Status
CANFD0_CH2_TURNA	0x40520530	FULL	TUR Numerator Actual
CANFD0_CH2_TTLGT	0x40520534	FULL	TT Local & Global Time
CANFD0_CH2_TTCTC	0x40520538	FULL	TT Cycle Time & Count
CANFD0_CH2_TTCPT	0x4052053C	FULL	TT Capture Time
CANFD0_CH2_TTCSCM	0x40520540	FULL	TT Cycle Sync Mark

2.1.4 CH 3

Register Name	Address	Permission	Description
CANFD0_CH3_RXFTOP_CTL	0x40520780	FULL	Receive FIFO Top control
CANFD0_CH3_RXFTOP0_STAT	0x405207A0	FULL	Receive FIFO 0 Top Status
CANFD0_CH3_RXFTOP0_DATA	0x405207A8	FULL	Receive FIFO 0 Top Data
CANFD0_CH3_RXFTOP1_STAT	0x405207B0	FULL	Receive FIFO 1 Top Status
CANFD0_CH3_RXFTOP1_DATA	0x405207B8	FULL	Receive FIFO 1 Top Data

2.1.4.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD0_CH3_CREL	0x40520600	FULL	Core Release Register

Register Name	Address	Permission	Description
CANFD0_CH3_ENDN	0x40520604	FULL	Endian Register
CANFD0_CH3_DBTP	0x4052060C	FULL	Data Bit Timing & Prescaler Register
CANFD0_CH3_TEST	0x40520610	FULL	Test Register
CANFD0_CH3_RWD	0x40520614	FULL	RAM Watchdog
CANFD0_CH3_CCCR	0x40520618	FULL	CC Control Register
CANFD0_CH3_NBTP	0x4052061C	FULL	Nominal Bit Timing & Prescaler Register
CANFD0_CH3_TSCC	0x40520620	FULL	Timestamp Counter Configuration
CANFD0_CH3_TSCV	0x40520624	FULL	Timestamp Counter Value
CANFD0_CH3_TOCC	0x40520628	FULL	Timeout Counter Configuration
CANFD0_CH3_TOCV	0x4052062C	FULL	Timeout Counter Value
CANFD0_CH3_ECR	0x40520640	FULL	Error Counter Register
CANFD0_CH3_PSR	0x40520644	FULL	Protocol Status Register
CANFD0_CH3_TDCR	0x40520648	FULL	Transmitter Delay Compensation Register
CANFD0_CH3_IR	0x40520650	FULL	Interrupt Register
CANFD0_CH3_IE	0x40520654	FULL	Interrupt Enable
CANFD0_CH3_ILS	0x40520658	FULL	Interrupt Line Select
CANFD0_CH3_ILE	0x4052065C	FULL	Interrupt Line Enable
CANFD0_CH3_GFC	0x40520680	FULL	Global Filter Configuration
CANFD0_CH3_SIDFC	0x40520684	FULL	Standard ID Filter Configuration
CANFD0_CH3_XIDFC	0x40520688	FULL	Extended ID Filter Configuration
CANFD0_CH3_XIDAM	0x40520690	FULL	Extended ID AND Mask
CANFD0_CH3_HPMS	0x40520694	FULL	High Priority Message Status
CANFD0_CH3_NDAT1	0x40520698	FULL	New Data 1
CANFD0_CH3_NDAT2	0x4052069C	FULL	New Data 2
CANFD0_CH3_RXF0C	0x405206A0	FULL	Rx FIFO 0 Configuration
CANFD0_CH3_RXF0S	0x405206A4	FULL	Rx FIFO 0 Status
CANFD0_CH3_RXF0A	0x405206A8	FULL	Rx FIFO 0 Acknowledge
CANFD0_CH3_RXBC	0x405206AC	FULL	Rx Buffer Configuration
CANFD0_CH3_RXF1C	0x405206B0	FULL	Rx FIFO 1 Configuration
CANFD0_CH3_RXF1S	0x405206B4	FULL	Rx FIFO 1 Status
CANFD0_CH3_RXF1A	0x405206B8	FULL	Rx FIFO 1 Acknowledge
CANFD0_CH3_RXESC	0x405206BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD0_CH3_TXBC	0x405206C0	FULL	Tx Buffer Configuration
CANFD0_CH3_TXFQS	0x405206C4	FULL	Tx FIFO/Queue Status
CANFD0_CH3_TXESC	0x405206C8	FULL	Tx Buffer Element Size Configuration
CANFD0_CH3_TXBRP	0x405206CC	FULL	Tx Buffer Request Pending
CANFD0_CH3_TXBAR	0x405206D0	FULL	Tx Buffer Add Request
CANFD0_CH3_TXBCR	0x405206D4	FULL	Tx Buffer Cancellation Request
CANFD0_CH3_TXBTO	0x405206D8	FULL	Tx Buffer Transmission Occurred
CANFD0_CH3_TXBCF	0x405206DC	FULL	Tx Buffer Cancellation Finished
CANFD0_CH3_TXBTIE	0x405206E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD0_CH3_TXBCIE	0x405206E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD0_CH3_TXEFC	0x405206F0	FULL	Tx Event FIFO Configuration
CANFD0_CH3_TXEFS	0x405206F4	FULL	Tx Event FIFO Status
CANFD0_CH3_TXEFA	0x405206F8	FULL	Tx Event FIFO Acknowledge
CANFD0_CH3_TTTMC	0x40520700	FULL	TT Trigger Memory Configuration
CANFD0_CH3_TTRMC	0x40520704	FULL	TT Reference Message Configuration
CANFD0_CH3_TTOCF	0x40520708	FULL	TT Operation Configuration
CANFD0_CH3_TTMLM	0x4052070C	FULL	TT Matrix Limits
CANFD0_CH3_TURCF	0x40520710	FULL	TUR Configuration
CANFD0_CH3_TTOCN	0x40520714	FULL	TT Operation Control
CANFD0_CH3_TTGTP	0x40520718	FULL	TT Global Time Preset
CANFD0_CH3_TTTMK	0x4052071C	FULL	TT Time Mark
CANFD0_CH3_TTIR	0x40520720	FULL	TT Interrupt Register
CANFD0_CH3_TTIE	0x40520724	FULL	TT Interrupt Enable
CANFD0_CH3_TTILS	0x40520728	FULL	TT Interrupt Line Select
CANFD0_CH3_TTOST	0x4052072C	FULL	TT Operation Status
CANFD0_CH3_TURNA	0x40520730	FULL	TUR Numerator Actual
CANFD0_CH3_TTLGT	0x40520734	FULL	TT Local & Global Time
CANFD0_CH3_TTCTC	0x40520738	FULL	TT Cycle Time & Count
CANFD0_CH3_TTCPT	0x4052073C	FULL	TT Capture Time
CANFD0_CH3_TTCSM	0x40520740	FULL	TT Cycle Sync Mark

2.2 CANFD 1

Description CAN Controller
Base Address 0x40540000
Size 0x20000
Slave Num MMIO5 - 2

Register Name	Address	Permission	Description
CANFD1_CTL	0x40541000	FULL	Global CAN control register
CANFD1_STATUS	0x40541004	FULL	Global CAN status register
CANFD1_INTR0_CAUSE	0x40541010	FULL	Consolidated interrupt0 cause register
CANFD1_INTR1_CAUSE	0x40541014	FULL	Consolidated interrupt1 cause register
CANFD1_ECC_CTL	0x40541080	FULL	ECC control
CANFD1_ECC_ERR_INJ	0x40541084	FULL	ECC error injection

2.2.1 CH 0

Register Name	Address	Permission	Description
CANFD1_CH0_RXFTOP_CTL	0x40540180	FULL	Receive FIFO Top control
CANFD1_CH0_RXFTOP0_STAT	0x405401A0	FULL	Receive FIFO 0 Top Status
CANFD1_CH0_RXFTOP0_DATA	0x405401A8	FULL	Receive FIFO 0 Top Data
CANFD1_CH0_RXFTOP1_STAT	0x405401B0	FULL	Receive FIFO 1 Top Status
CANFD1_CH0_RXFTOP1_DATA	0x405401B8	FULL	Receive FIFO 1 Top Data

2.2.1.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD1_CH0_CREL	0x40540000	FULL	Core Release Register
CANFD1_CH0_ENDN	0x40540004	FULL	Endian Register
CANFD1_CH0_DBTP	0x4054000C	FULL	Data Bit Timing & Prescaler Register
CANFD1_CH0_TEST	0x40540010	FULL	Test Register
CANFD1_CH0_RWD	0x40540014	FULL	RAM Watchdog
CANFD1_CH0_CCCR	0x40540018	FULL	CC Control Register
CANFD1_CH0_NBTP	0x4054001C	FULL	Nominal Bit Timing & Prescaler Register
CANFD1_CH0_TSCC	0x40540020	FULL	Timestamp Counter Configuration
CANFD1_CH0_TSCV	0x40540024	FULL	Timestamp Counter Value
CANFD1_CH0_TOCC	0x40540028	FULL	Timeout Counter Configuration
CANFD1_CH0_TOCV	0x4054002C	FULL	Timeout Counter Value
CANFD1_CH0_ECR	0x40540040	FULL	Error Counter Register
CANFD1_CH0_PSR	0x40540044	FULL	Protocol Status Register
CANFD1_CH0_TDCR	0x40540048	FULL	Transmitter Delay Compensation Register
CANFD1_CH0_IR	0x40540050	FULL	Interrupt Register
CANFD1_CH0_IE	0x40540054	FULL	Interrupt Enable
CANFD1_CH0_ILS	0x40540058	FULL	Interrupt Line Select
CANFD1_CH0_ILE	0x4054005C	FULL	Interrupt Line Enable
CANFD1_CH0_GFC	0x40540080	FULL	Global Filter Configuration
CANFD1_CH0_SIDFC	0x40540084	FULL	Standard ID Filter Configuration
CANFD1_CH0_XIDFC	0x40540088	FULL	Extended ID Filter Configuration
CANFD1_CH0_XIDAM	0x40540090	FULL	Extended ID AND Mask
CANFD1_CH0_HPMS	0x40540094	FULL	High Priority Message Status
CANFD1_CH0_NDAT1	0x40540098	FULL	New Data 1
CANFD1_CH0_NDAT2	0x4054009C	FULL	New Data 2
CANFD1_CH0_RXF0C	0x405400A0	FULL	Rx FIFO 0 Configuration
CANFD1_CH0_RXF0S	0x405400A4	FULL	Rx FIFO 0 Status
CANFD1_CH0_RXF0A	0x405400A8	FULL	Rx FIFO 0 Acknowledge
CANFD1_CH0_RXBC	0x405400AC	FULL	Rx Buffer Configuration
CANFD1_CH0_RXF1C	0x405400B0	FULL	Rx FIFO 1 Configuration
CANFD1_CH0_RXF1S	0x405400B4	FULL	Rx FIFO 1 Status
CANFD1_CH0_RXF1A	0x405400B8	FULL	Rx FIFO 1 Acknowledge
CANFD1_CH0_RXESC	0x405400BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD1_CH0_TXBC	0x405400C0	FULL	Tx Buffer Configuration
CANFD1_CH0_TXFQS	0x405400C4	FULL	Tx FIFO/Queue Status
CANFD1_CH0_TXESC	0x405400C8	FULL	Tx Buffer Element Size Configuration
CANFD1_CH0_TXBRP	0x405400CC	FULL	Tx Buffer Request Pending
CANFD1_CH0_TXBAR	0x405400D0	FULL	Tx Buffer Add Request

Register Name	Address	Permission	Description
CANFD1_CH0_TXBCR	0x405400D4	FULL	Tx Buffer Cancellation Request
CANFD1_CH0_TXBTO	0x405400D8	FULL	Tx Buffer Transmission Occurred
CANFD1_CH0_TXBCF	0x405400DC	FULL	Tx Buffer Cancellation Finished
CANFD1_CH0_TXBTIE	0x405400E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD1_CH0_TXBCIE	0x405400E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD1_CH0_TXEFC	0x405400F0	FULL	Tx Event FIFO Configuration
CANFD1_CH0_TXEFS	0x405400F4	FULL	Tx Event FIFO Status
CANFD1_CH0_TXEFA	0x405400F8	FULL	Tx Event FIFO Acknowledge
CANFD1_CH0_TTTMC	0x40540100	FULL	TT Trigger Memory Configuration
CANFD1_CH0_TTRMC	0x40540104	FULL	TT Reference Message Configuration
CANFD1_CH0_TTOCF	0x40540108	FULL	TT Operation Configuration
CANFD1_CH0_TTMLM	0x4054010C	FULL	TT Matrix Limits
CANFD1_CH0_TURCF	0x40540110	FULL	TUR Configuration
CANFD1_CH0_TTOCN	0x40540114	FULL	TT Operation Control
CANFD1_CH0_TTGTP	0x40540118	FULL	TT Global Time Preset
CANFD1_CH0_TTTMK	0x4054011C	FULL	TT Time Mark
CANFD1_CH0_TTIR	0x40540120	FULL	TT Interrupt Register
CANFD1_CH0_TTIE	0x40540124	FULL	TT Interrupt Enable
CANFD1_CH0_TTILS	0x40540128	FULL	TT Interrupt Line Select
CANFD1_CH0_TTOST	0x4054012C	FULL	TT Operation Status
CANFD1_CH0_TURNA	0x40540130	FULL	TUR Numerator Actual
CANFD1_CH0_TTLGT	0x40540134	FULL	TT Local & Global Time
CANFD1_CH0_TTCTC	0x40540138	FULL	TT Cycle Time & Count
CANFD1_CH0_TTCPT	0x4054013C	FULL	TT Capture Time
CANFD1_CH0_TTCSM	0x40540140	FULL	TT Cycle Sync Mark

2.2.2 CH 1

Register Name	Address	Permission	Description
CANFD1_CH1_RXFTOP_CTL	0x40540380	FULL	Receive FIFO Top control
CANFD1_CH1_RXFTOP0_STAT	0x405403A0	FULL	Receive FIFO 0 Top Status
CANFD1_CH1_RXFTOP0_DATA	0x405403A8	FULL	Receive FIFO 0 Top Data
CANFD1_CH1_RXFTOP1_STAT	0x405403B0	FULL	Receive FIFO 1 Top Status
CANFD1_CH1_RXFTOP1_DATA	0x405403B8	FULL	Receive FIFO 1 Top Data

2.2.2.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD1_CH1_CREL	0x40540200	FULL	Core Release Register
CANFD1_CH1_ENDN	0x40540204	FULL	Endian Register
CANFD1_CH1_DBTP	0x4054020C	FULL	Data Bit Timing & Prescaler Register
CANFD1_CH1_TEST	0x40540210	FULL	Test Register
CANFD1_CH1_RWD	0x40540214	FULL	RAM Watchdog
CANFD1_CH1_CCCR	0x40540218	FULL	CC Control Register
CANFD1_CH1_NBTP	0x4054021C	FULL	Nominal Bit Timing & Prescaler Register
CANFD1_CH1_TSCC	0x40540220	FULL	Timestamp Counter Configuration
CANFD1_CH1_TSCV	0x40540224	FULL	Timestamp Counter Value
CANFD1_CH1_TOCC	0x40540228	FULL	Timeout Counter Configuration
CANFD1_CH1_TOCV	0x4054022C	FULL	Timeout Counter Value
CANFD1_CH1_ECR	0x40540240	FULL	Error Counter Register
CANFD1_CH1_PSR	0x40540244	FULL	Protocol Status Register
CANFD1_CH1_TDCR	0x40540248	FULL	Transmitter Delay Compensation Register
CANFD1_CH1_IR	0x40540250	FULL	Interrupt Register
CANFD1_CH1_IE	0x40540254	FULL	Interrupt Enable
CANFD1_CH1_ILS	0x40540258	FULL	Interrupt Line Select
CANFD1_CH1_IJE	0x4054025C	FULL	Interrupt Line Enable
CANFD1_CH1_GFC	0x40540280	FULL	Global Filter Configuration
CANFD1_CH1_SIDFC	0x40540284	FULL	Standard ID Filter Configuration
CANFD1_CH1_XIDFC	0x40540288	FULL	Extended ID Filter Configuration
CANFD1_CH1_XIDAM	0x40540290	FULL	Extended ID AND Mask
CANFD1_CH1_HPMS	0x40540294	FULL	High Priority Message Status
CANFD1_CH1_NDAT1	0x40540298	FULL	New Data 1
CANFD1_CH1_NDAT2	0x4054029C	FULL	New Data 2
CANFD1_CH1_RXF0C	0x405402A0	FULL	Rx FIFO 0 Configuration
CANFD1_CH1_RXF0S	0x405402A4	FULL	Rx FIFO 0 Status

Register Name	Address	Permission	Description
CANFD1_CH1_RXF0A	0x405402A8	FULL	Rx FIFO 0 Acknowledge
CANFD1_CH1_RXBC	0x405402AC	FULL	Rx Buffer Configuration
CANFD1_CH1_RXF1C	0x405402B0	FULL	Rx FIFO 1 Configuration
CANFD1_CH1_RXF1S	0x405402B4	FULL	Rx FIFO 1 Status
CANFD1_CH1_RXF1A	0x405402B8	FULL	Rx FIFO 1 Acknowledge
CANFD1_CH1_RXESC	0x405402BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD1_CH1_TXBC	0x405402C0	FULL	Tx Buffer Configuration
CANFD1_CH1_TXFQS	0x405402C4	FULL	Tx FIFO/Queue Status
CANFD1_CH1_TXESC	0x405402C8	FULL	Tx Buffer Element Size Configuration
CANFD1_CH1_TXBRP	0x405402CC	FULL	Tx Buffer Request Pending
CANFD1_CH1_TXBAR	0x405402D0	FULL	Tx Buffer Add Request
CANFD1_CH1_TXBCR	0x405402D4	FULL	Tx Buffer Cancellation Request
CANFD1_CH1_TXBTO	0x405402D8	FULL	Tx Buffer Transmission Occurred
CANFD1_CH1_TXBCF	0x405402DC	FULL	Tx Buffer Cancellation Finished
CANFD1_CH1_TXBTIE	0x405402E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD1_CH1_TXBCIE	0x405402E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD1_CH1_TXEFC	0x405402F0	FULL	Tx Event FIFO Configuration
CANFD1_CH1_TXEFS	0x405402F4	FULL	Tx Event FIFO Status
CANFD1_CH1_TXEFA	0x405402F8	FULL	Tx Event FIFO Acknowledge
CANFD1_CH1_TTTMC	0x40540300	FULL	TT Trigger Memory Configuration
CANFD1_CH1_TTRMC	0x40540304	FULL	TT Reference Message Configuration
CANFD1_CH1_TTOCF	0x40540308	FULL	TT Operation Configuration
CANFD1_CH1_TTMLM	0x4054030C	FULL	TT Matrix Limits
CANFD1_CH1_TURCF	0x40540310	FULL	TUR Configuration
CANFD1_CH1_TTOCN	0x40540314	FULL	TT Operation Control
CANFD1_CH1_TTGTP	0x40540318	FULL	TT Global Time Preset
CANFD1_CH1_TTTMK	0x4054031C	FULL	TT Time Mark
CANFD1_CH1_TTIR	0x40540320	FULL	TT Interrupt Register
CANFD1_CH1_TTIE	0x40540324	FULL	TT Interrupt Enable
CANFD1_CH1_TTILS	0x40540328	FULL	TT Interrupt Line Select
CANFD1_CH1_TTOST	0x4054032C	FULL	TT Operation Status
CANFD1_CH1_TURNA	0x40540330	FULL	TUR Numerator Actual
CANFD1_CH1_TTLGT	0x40540334	FULL	TT Local & Global Time
CANFD1_CH1_TTCTC	0x40540338	FULL	TT Cycle Time & Count
CANFD1_CH1_TTCPT	0x4054033C	FULL	TT Capture Time
CANFD1_CH1_TTCSM	0x40540340	FULL	TT Cycle Sync Mark

2.2.3 CH 2

Register Name	Address	Permission	Description
CANFD1_CH2_RXFTOP_CTL	0x40540580	FULL	Receive FIFO Top control
CANFD1_CH2_RXFTOP0_STAT	0x405405A0	FULL	Receive FIFO 0 Top Status
CANFD1_CH2_RXFTOP0_DATA	0x405405A8	FULL	Receive FIFO 0 Top Data
CANFD1_CH2_RXFTOP1_STAT	0x405405B0	FULL	Receive FIFO 1 Top Status
CANFD1_CH2_RXFTOP1_DATA	0x405405B8	FULL	Receive FIFO 1 Top Data

2.2.3.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD1_CH2_CREL	0x40540400	FULL	Core Release Register
CANFD1_CH2_ENDN	0x40540404	FULL	Endian Register
CANFD1_CH2_DBTP	0x4054040C	FULL	Data Bit Timing & Prescaler Register
CANFD1_CH2_TEST	0x40540410	FULL	Test Register
CANFD1_CH2_RWD	0x40540414	FULL	RAM Watchdog
CANFD1_CH2_CCCR	0x40540418	FULL	CC Control Register
CANFD1_CH2_NBTP	0x4054041C	FULL	Nominal Bit Timing & Prescaler Register
CANFD1_CH2_TSCC	0x40540420	FULL	Timestamp Counter Configuration
CANFD1_CH2_TSCV	0x40540424	FULL	Timestamp Counter Value
CANFD1_CH2_TOCC	0x40540428	FULL	Timeout Counter Configuration
CANFD1_CH2_TOCV	0x4054042C	FULL	Timeout Counter Value
CANFD1_CH2_ECR	0x40540440	FULL	Error Counter Register
CANFD1_CH2_PSR	0x40540444	FULL	Protocol Status Register
CANFD1_CH2_TDCR	0x40540448	FULL	Transmitter Delay Compensation Register
CANFD1_CH2_IR	0x40540450	FULL	Interrupt Register
CANFD1_CH2_IE	0x40540454	FULL	Interrupt Enable

Register Name	Address	Permission	Description
CANFD1_CH2_ILS	0x40540458	FULL	Interrupt Line Select
CANFD1_CH2_ILE	0x4054045C	FULL	Interrupt Line Enable
CANFD1_CH2_GFC	0x40540480	FULL	Global Filter Configuration
CANFD1_CH2_SIDFC	0x40540484	FULL	Standard ID Filter Configuration
CANFD1_CH2_XIDFC	0x40540488	FULL	Extended ID Filter Configuration
CANFD1_CH2_XIDAM	0x40540490	FULL	Extended ID AND Mask
CANFD1_CH2_HPMS	0x40540494	FULL	High Priority Message Status
CANFD1_CH2_NDAT1	0x40540498	FULL	New Data 1
CANFD1_CH2_NDAT2	0x4054049C	FULL	New Data 2
CANFD1_CH2_RXF0C	0x405404A0	FULL	Rx FIFO 0 Configuration
CANFD1_CH2_RXF0S	0x405404A4	FULL	Rx FIFO 0 Status
CANFD1_CH2_RXF0A	0x405404A8	FULL	Rx FIFO 0 Acknowledge
CANFD1_CH2_RXBC	0x405404AC	FULL	Rx Buffer Configuration
CANFD1_CH2_RXF1C	0x405404B0	FULL	Rx FIFO 1 Configuration
CANFD1_CH2_RXF1S	0x405404B4	FULL	Rx FIFO 1 Status
CANFD1_CH2_RXF1A	0x405404B8	FULL	Rx FIFO 1 Acknowledge
CANFD1_CH2_RXESC	0x405404BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD1_CH2_TXBC	0x405404C0	FULL	Tx Buffer Configuration
CANFD1_CH2_TXFQS	0x405404C4	FULL	Tx FIFO/Queue Status
CANFD1_CH2_TXESC	0x405404C8	FULL	Tx Buffer Element Size Configuration
CANFD1_CH2_TXBRP	0x405404CC	FULL	Tx Buffer Request Pending
CANFD1_CH2_TXBAR	0x405404D0	FULL	Tx Buffer Add Request
CANFD1_CH2_TXBCR	0x405404D4	FULL	Tx Buffer Cancellation Request
CANFD1_CH2_TXBTO	0x405404D8	FULL	Tx Buffer Transmission Occurred
CANFD1_CH2_TXBCF	0x405404DC	FULL	Tx Buffer Cancellation Finished
CANFD1_CH2_TXBTIE	0x405404E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD1_CH2_TXBCIE	0x405404E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD1_CH2_TXEFC	0x405404F0	FULL	Tx Event FIFO Configuration
CANFD1_CH2_TXEFS	0x405404F4	FULL	Tx Event FIFO Status
CANFD1_CH2_TXEFA	0x405404F8	FULL	Tx Event FIFO Acknowledge
CANFD1_CH2_TTTMC	0x40540500	FULL	TT Trigger Memory Configuration
CANFD1_CH2_TTRMC	0x40540504	FULL	TT Reference Message Configuration
CANFD1_CH2_TTOCF	0x40540508	FULL	TT Operation Configuration
CANFD1_CH2_TTMLM	0x4054050C	FULL	TT Matrix Limits
CANFD1_CH2_TURCF	0x40540510	FULL	TUR Configuration
CANFD1_CH2_TTOCN	0x40540514	FULL	TT Operation Control
CANFD1_CH2_TTGRP	0x40540518	FULL	TT Global Time Preset
CANFD1_CH2_TTTMK	0x4054051C	FULL	TT Time Mark
CANFD1_CH2_TTIR	0x40540520	FULL	TT Interrupt Register
CANFD1_CH2_TTIE	0x40540524	FULL	TT Interrupt Enable
CANFD1_CH2_TTILS	0x40540528	FULL	TT Interrupt Line Select
CANFD1_CH2_TTOST	0x4054052C	FULL	TT Operation Status
CANFD1_CH2_TURNA	0x40540530	FULL	TUR Numerator Actual
CANFD1_CH2_TTLGT	0x40540534	FULL	TT Local & Global Time
CANFD1_CH2_TTCTC	0x40540538	FULL	TT Cycle Time & Count
CANFD1_CH2_TTCPT	0x4054053C	FULL	TT Capture Time
CANFD1_CH2_TTCSM	0x40540540	FULL	TT Cycle Sync Mark

2.2.4 CH 3

Register Name	Address	Permission	Description
CANFD1_CH3_RXFTOP_CTL	0x40540780	FULL	Receive FIFO Top control
CANFD1_CH3_RXFTOP0_STAT	0x405407A0	FULL	Receive FIFO 0 Top Status
CANFD1_CH3_RXFTOP0_DATA	0x405407A8	FULL	Receive FIFO 0 Top Data
CANFD1_CH3_RXFTOP1_STAT	0x405407B0	FULL	Receive FIFO 1 Top Status
CANFD1_CH3_RXFTOP1_DATA	0x405407B8	FULL	Receive FIFO 1 Top Data

2.2.4.1 M_TTCAN

Register Name	Address	Permission	Description
CANFD1_CH3_CREL	0x40540600	FULL	Core Release Register
CANFD1_CH3_ENDN	0x40540604	FULL	Endian Register
CANFD1_CH3_DBTP	0x4054060C	FULL	Data Bit Timing & Prescaler Register
CANFD1_CH3_TEST	0x40540610	FULL	Test Register
CANFD1_CH3_RWD	0x40540614	FULL	RAM Watchdog

Register Name	Address	Permission	Description
CANFD1_CH3_CCCR	0x40540618	FULL	CC Control Register
CANFD1_CH3_NBTP	0x4054061C	FULL	Nominal Bit Timing & Prescaler Register
CANFD1_CH3_TSCC	0x40540620	FULL	Timestamp Counter Configuration
CANFD1_CH3_TSCV	0x40540624	FULL	Timestamp Counter Value
CANFD1_CH3_TOCC	0x40540628	FULL	Timeout Counter Configuration
CANFD1_CH3_TOCV	0x4054062C	FULL	Timeout Counter Value
CANFD1_CH3_ECR	0x40540640	FULL	Error Counter Register
CANFD1_CH3_PSR	0x40540644	FULL	Protocol Status Register
CANFD1_CH3_TDCR	0x40540648	FULL	Transmitter Delay Compensation Register
CANFD1_CH3_IR	0x40540650	FULL	Interrupt Register
CANFD1_CH3_IE	0x40540654	FULL	Interrupt Enable
CANFD1_CH3_ILS	0x40540658	FULL	Interrupt Line Select
CANFD1_CH3_ILE	0x4054065C	FULL	Interrupt Line Enable
CANFD1_CH3_GFC	0x40540680	FULL	Global Filter Configuration
CANFD1_CH3_SIDFC	0x40540684	FULL	Standard ID Filter Configuration
CANFD1_CH3_XIDFC	0x40540688	FULL	Extended ID Filter Configuration
CANFD1_CH3_XIDAM	0x40540690	FULL	Extended ID AND Mask
CANFD1_CH3_HPMS	0x40540694	FULL	High Priority Message Status
CANFD1_CH3_NDAT1	0x40540698	FULL	New Data 1
CANFD1_CH3_NDAT2	0x4054069C	FULL	New Data 2
CANFD1_CH3_RXF0C	0x405406A0	FULL	Rx FIFO 0 Configuration
CANFD1_CH3_RXF0S	0x405406A4	FULL	Rx FIFO 0 Status
CANFD1_CH3_RXF0A	0x405406A8	FULL	Rx FIFO 0 Acknowledge
CANFD1_CH3_RXBC	0x405406AC	FULL	Rx Buffer Configuration
CANFD1_CH3_RXF1C	0x405406B0	FULL	Rx FIFO 1 Configuration
CANFD1_CH3_RXF1S	0x405406B4	FULL	Rx FIFO 1 Status
CANFD1_CH3_RXF1A	0x405406B8	FULL	Rx FIFO 1 Acknowledge
CANFD1_CH3_RXESC	0x405406BC	FULL	Rx Buffer / FIFO Element Size Configuration
CANFD1_CH3_TXBC	0x405406C0	FULL	Tx Buffer Configuration
CANFD1_CH3_TXFQS	0x405406C4	FULL	Tx FIFO/Queue Status
CANFD1_CH3_TXESC	0x405406C8	FULL	Tx Buffer Element Size Configuration
CANFD1_CH3_TXBRP	0x405406CC	FULL	Tx Buffer Request Pending
CANFD1_CH3_TXBAR	0x405406D0	FULL	Tx Buffer Add Request
CANFD1_CH3_TXBCR	0x405406D4	FULL	Tx Buffer Cancellation Request
CANFD1_CH3_TXBTO	0x405406D8	FULL	Tx Buffer Transmission Occurred
CANFD1_CH3_TXBCF	0x405406DC	FULL	Tx Buffer Cancellation Finished
CANFD1_CH3_TXBTIE	0x405406E0	FULL	Tx Buffer Transmission Interrupt Enable
CANFD1_CH3_TXBCIE	0x405406E4	FULL	Tx Buffer Cancellation Finished Interrupt Enable
CANFD1_CH3_TXEFC	0x405406F0	FULL	Tx Event FIFO Configuration
CANFD1_CH3_TXEFS	0x405406F4	FULL	Tx Event FIFO Status
CANFD1_CH3_TXEFA	0x405406F8	FULL	Tx Event FIFO Acknowledge
CANFD1_CH3_TTTMC	0x40540700	FULL	TT Trigger Memory Configuration
CANFD1_CH3_TTRMC	0x40540704	FULL	TT Reference Message Configuration
CANFD1_CH3_TTOCF	0x40540708	FULL	TT Operation Configuration
CANFD1_CH3_TTMLM	0x4054070C	FULL	TT Matrix Limits
CANFD1_CH3_TURCF	0x40540710	FULL	TUR Configuration
CANFD1_CH3_TTOCN	0x40540714	FULL	TT Operation Control
CANFD1_CH3_TTGTP	0x40540718	FULL	TT Global Time Preset
CANFD1_CH3_TTTMK	0x4054071C	FULL	TT Time Mark
CANFD1_CH3_TTIR	0x40540720	FULL	TT Interrupt Register
CANFD1_CH3_TTIE	0x40540724	FULL	TT Interrupt Enable
CANFD1_CH3_TTILS	0x40540728	FULL	TT Interrupt Line Select
CANFD1_CH3_TTOST	0x4054072C	FULL	TT Operation Status
CANFD1_CH3_TURNA	0x40540730	FULL	TUR Numerator Actual
CANFD1_CH3_TTLGT	0x40540734	FULL	TT Local & Global Time
CANFD1_CH3_TTCTC	0x40540738	FULL	TT Cycle Time & Count
CANFD1_CH3_TTCPT	0x4054073C	FULL	TT Capture Time
CANFD1_CH3_TTCSM	0x40540740	FULL	TT Cycle Sync Mark

2.3 Register Details

2.3.1 CANFD_CTL

Description: Global CAN control register
Address: 0x40521000
Offset: 0x1000
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STOP_REQ [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	MRAM_OFF [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	STOP_REQ	RW	RW	0	Clock Stop Request for each TTCAN IP . The m_ttcn_clkstop_req of each TTCAN IP is directly driven by these bits.
31	MRAM_OFF	RW	RW	0	MRAM off 0= Default MRAM on (with MRAM retained in DeepSleep). 1= Switch MRAM off (not retained) to save power. Before setting this bit all the CAN channels have to be powered down using the STOP_REQ/ACK bits. When the MRAM is off any access attempt to it is considered an address error (as if MRAM_SIZE=0). After switching the MRAM on again software needs to allow for a certain power up time before MRAM can be used, i.e. before STOP_REQ can be de-asserted. The power up time is equivalent to the system SRAM power up time specified in the CPUSS.RAM_PWR_DELAY_CTL register. To meet S8 platform requirements, MRAM_OFF should be set to 0 prior to transitioning to Hibernate mode.

2.3.2 CANFD_STATUS

Description: Global CAN status register
Address: 0x40521004
Offset: 0x1004
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STOP_ACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	STOP_ACK	R	R	0	Clock Stop Acknowledge for each TTCAN IP. These bits are directly driven by m_tcan_clkstop_ack of each TTCAN IP. When this bit is set the corresponding TTCAN IP clocks will be gated off, except HCLK will be enabled for each AHB write

2.3.3 CANFD_INTRO_CAUSE

Description: Consolidated interrupt0 cause register
Address: 0x40521010
Offset: 0x1010
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INT0	R	R	0	Show pending m_ttcan_int0 of each channel

2.3.4 CANFD_INTR1_CAUSE

Description: Consolidated interrupt1 cause register
Address: 0x40521014
Offset: 0x1014
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT1 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INT1	R	R	0	Show pending m_ttcan_int1 of each channel

2.3.5 CANFD_TS_CTL

Description: Time Stamp control register
Address: 0x40521020
Offset: 0x1020
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PRESCALE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	PRESCALE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	PRESCALE	RW	RW	0	Time Stamp counter prescale value. When enabled divide the Host clock (HCLK) by PRESCALE+1 to create Time Stamp clock ticks.
31	ENABLED	RW	RW	0	Counter enable bit 0 = Count disabled. Stop counting up and keep the counter value 1 = Count enabled. Start counting up from the current value

2.3.6 CANFD_TS_CNT

Description: Time Stamp counter value
Address: 0x40521024
Offset: 0x1024
Retention: Not Retained
IsDeepSleep: No
Comment: Not retained
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VALUE	RW	RW	0	The counter value of the Time Stamp Counter. When enabled this counter will count Time Stamp clock ticks from the pre-scaler. When written this counter and the pre-scaler will reset to 0 (write data is ignored).

2.3.7 CANFD_ECC_CTL

Description: ECC control
Address: 0x40521080
Offset: 0x1080
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							ECC_EN [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16	ECC_EN	RW	RW	0	Enable ECC for CANFD SRAM When disabled also all error injection functionality is disabled.

2.3.8 CANFD_ECC_ERR_INJ

Description: ECC error injection
Address: 0x40521084
Offset: 0x1084
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFC

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	ERR_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			ERR_EN [20:20]	None [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	ERR_PAR [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	ERR_ADDR	RW	RW	16383	Specifies the address of the word where an error will be injected on write or a non-correctable error will be suppressed. When the ERR_EN bit is set an error parity (ERR_PAR) is injected when any write, from bus or a CAN channel, is done to this address. When the ERR_EN bit is set and the access address matches ERR_ADDR then a non-correctable ECC error or an Address error will NOT result in a bus error or CAN channel shutdown. Note that error reporting to the fault structure cannot be suppressed.
20	ERR_EN	RW	RW	0	Enable error injection (ECC_EN must be 1). When this bit is set the error parity (ERR_PAR) will be used when an AHB write is done to the ERR_ADDR address. When the error word is read a single or double error will be reported to the fault structure just like for a real ECC error (even if this bit is no longer set). When this bit is set (and ECC_EN=1) a non-correctable error (ECC or address error) for the ERR_ADDR will not be reported back to the CAN channel or AHB bus.
24:30	ERR_PAR	RW	RW	0	ECC Parity bits to use for ECC error injection at address ERR_ADDR.

2.3.9 CH

2.3.9.1 CANFD_CH_RXFTOP_CTL

Description: Receive FIFO Top control
Address: 0x40520180
Offset: 0x180
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						F1TPE [1:1]	F0TPE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	F0TPE	RW	RW	0	FIFO 0 Top Pointer Enable. This enables the FIFO top pointer logic to set the FIFO Top Address (FnTA) and message word counter. This logic is also disabled when the IP is being reconfigured (CCCR.CCE=1). When this logic is disabled a Read from RXFTOP0_DATA is undefined.
1	F1TPE	RW	RW	0	FIFO 1 Top Pointer Enable.

2.3.9.2 CANFD_CH_RXFTOP0_STAT

Description: Receive FIFO 0 Top Status
Address: 0x405201A0
Offset: 0x1A0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	F0TA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	F0TA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	F0TA	R	R	0	Current FIFO 0 Top Address. This is a pointer to the next word in the message buffer defined by the FIFO Start Address (FnSA), Get Index (FnGI), the FIFO message size (FnDS) and the message word counter (FnMWC) $FnTA = FnSA + FnGI * msg\_size[FnDS] + FnMWC$

2.3.9.3 CANFD_CH_RXFTOP0_DATA

Description: Receive FIFO 0 Top Data
Address: 0x405201A8
Offset: 0x1A8
Retention: Retained
IsDeepSleep: No
Comment: Read side effect, except if read from debug host
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	F0TD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	F0TD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	F0TD [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	F0TD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	F0TD	R	R	Undefined	When enabled (F0TPE=1) read data from MRAM at location FnTA. This register can have a read side effect if the following conditions are met: - M_TTCAN not being reconfigured (CCCR.CCE=0) - FIFO Top Pointer logic is enabled (FnTPE=1) - FIFO is not empty (FnFL!=0) The read side effect is as follows: - if FnMWC pointed to the last word of the message (as indicated by FnDS) then the corresponding message index (FnGI) is automatically acknowledge by a write to FnAI - FnMWC is incremented (or restarted if FnMWC pointed to the last word of the message) - the FIFO top address FnTA is incremented (with FIFO wrap around) When this logic is disabled (F0TPE=0) a Read from this register returns undefined data.

2.3.9.4 CANFD_CH_RXFTOP1_STAT

Description: Receive FIFO 1 Top Status
Address: 0x405201B0
Offset: 0x1B0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	F1TA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	F1TA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	F1TA	R	R	0	See F0TA description

2.3.9.5 CANFD_CH_RXFTOP1_DATA

Description: Receive FIFO 1 Top Data
Address: 0x405201B8
Offset: 0x1B8
Retention: Retained
IsDeepSleep: No
Comment: Read side effect, except if read from debug host
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	F1TD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	F1TD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	F1TD [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	F1TD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	F1TD	R	R	Undefined	See F0TD description

2.3.9.6 M_TTCAN

2.3.9.6.1 CANFD_CH_CREL

Description: Core Release Register
Address: 0x40520000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DAY [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MON [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	SUBSTEP [23:20]				YEAR [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	REL [31:28]				STEP [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DAY	R	R	0	Time Stamp Day Two digits, BCD-coded. This field is set by generic parameter on M_TTCAN synthesis.
8:15	MON	R	R	0	Time Stamp Month Two digits, BCD-coded. This field is set by generic parameter on M_TTCAN synthesis.
16:19	YEAR	R	R	0	Time Stamp Year One digit, BCD-coded. This field is set by generic parameter on M_TTCAN synthesis.
20:23	SUBSTEP	R	R	0	Sub-step of Core Release One digit, BCD-coded.
24:27	STEP	R	R	0	Step of Core Release One digit, BCD-coded.
28:31	REL	R	R	0	Core Release One digit, BCD-coded.

2.3.9.6.2 CANFD_CH_ENDN

Description: Endian Register
Address: 0x40520004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x87654321

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ETV [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ETV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ETV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ETV [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ETV	R	R	227156048 1	Endianness Test Value The endianness test value is 0x87654321.

2.3.9.6.3 CANFD_CH_DBTP

Description: Data Bit Timing & Prescaler Register
Address: 0x4052000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Protected Write
Default: 0xA33

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DTSEG2 [7:4]				DSJW [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DTSEG1 [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	TDC [23:23]	None [22:21]		DBRP [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	DSJW	RW	RW	3	Data (Re)Synchronization Jump Width 0x0-0xF Valid values are 0 to 15. The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
4:7	DTSEG2	RW	RW	3	Data time segment after sample point 0x0-0xF Valid values are 0 to 15. The actual interpretation by the hardware of this value is such that one more than the programmed value is used.
8:12	DTSEG1	RW	RW	10	Data time segment before sample point 0x00-0x1F Valid values are 0 to 31. The actual interpretation by the hardware of this value is such that one more than the programmed value is used.
16:20	DBRP	RW	RW	0	Data Bit Rate Prescaler 0x00-0x1F The value by which the oscillator frequency is divided for generating the bit time quanta. The bit time is built up from a multiple of this quanta. Valid values for the Bit Rate Prescaler are 0 to 31. The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
23	TDC	RW	RW	0	Transmitter Delay Compensation 0= Transmitter Delay Compensation disabled 1= Transmitter Delay Compensation enabled

2.3.9.6.4 CANFD_CH_TEST

Description: Test Register
Address: 0x40520010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Protected Write
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RX [7:7]	TX [6:5]		LBCK [4:4]	CAT [3:3]	CAM [2:2]	TAT [1:1]	TAM [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TAM	RW	RW	0	ASC is not supported by M_TTCAN Test ASC Multiplexer Control Controls output pin m_ttcn_ascm in test mode, ORed with the signal from the FSE 0= Level at pin m_ttcn_ascm controlled by FSE 1= Level at pin m_ttcn_ascm = '1'
1	TAT	RW	RW	0	ASC is not supported by M_TTCAN Test ASC Transmit Control Controls output pin m_ttcn_asct in test mode, ORed with the signal from the FSE 0= Level at pin m_ttcn_asct controlled by FSE 1= Level at pin m_ttcn_asct = '1'
2	CAM	RW	RW	0	ASC is not supported by M_TTCAN Check ASC Multiplexer Control Monitors level at output pin m_ttcn_ascm. 0= Output pin m_ttcn_ascm = '0' 1= Output pin m_ttcn_ascm = '1'
3	CAT	RW	RW	0	ASC is not supported by M_TTCAN Check ASC Transmit Control Monitors level at output pin m_ttcn_asct. 0= Output pin m_ttcn_asct = '0'
4	LBCK	RW	RW	0	Loop Back Mode 0= Reset value, Loop Back Mode is disabled 1= Loop Back Mode is enabled (see Section 3.1.9, Test Modes)
5:6	TX	RW	RW	0	Control of Transmit Pin 00 Reset value, m_ttcn_tx controlled by the CAN Core, updated at the end of the CAN bit time 01 Sample Point can be monitored at pin m_ttcn_tx 10 Dominant ('0') level at pin m_ttcn_tx 11 Recessive ('1') at pin m_ttcn_tx
7	RX	R	R	Undefined	Receive Pin Monitors the actual value of pin m_ttcn_rx 0= The CAN bus is dominant (m_ttcn_rx = '0') 1= The CAN bus is recessive (m_ttcn_rx = '1')

2.3.9.6.5 CANFD_CH_RWD

Description: RAM Watchdog
Address: 0x40520014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: Protected Write
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WDC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	WDV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	WDC	RW	RW	0	Watchdog Configuration Start value of the Message RAM Watchdog Counter. With the reset value of '00' the counter is disabled.
8:15	WDV	R	R	0	Watchdog Value Actual Message RAM Watchdog Counter Value.

2.3.9.6.6 CANFD_CH_CCCR

Description: CC Control Register
Address: 0x40520018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: Protected Write
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TEST [7:7]	DAR [6:6]	MON_ [5:5]	CSR [4:4]	CSA [3:3]	ASM [2:2]	CCE [1:1]	INIT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	NISO [15:15]	TXP [14:14]	EFBI [13:13]	PXHD [12:12]	None [11:10]		BRSE [9:9]	FDOE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INIT	RW	RW	1	Initialization 0= Normal Operation 1= Initialization is started
1	CCE	RW	RW	0	Configuration Change Enable 0= The CPU has no write access to the protected configuration registers 1= The CPU has write access to the protected configuration registers (while CCCR.INIT = '1')
2	ASM	RW	RW	0	Restricted Operation Mode Bit ASM can only be set by the Host when both CCE and INIT are set to '1'. The bit can be reset by the Host at any time. For a description of the Restricted Operation Mode see Section 3.1.5. 0= Normal CAN operation 1= Restricted Operation Mode active
3	CSA	RW	RW	0	Clock Stop Acknowledge 0= No clock stop acknowledged 1= M_TTCAN may be set in power down by stopping m_ttcn_hclk and m_ttcn_cclk
4	CSR	RW	RW	0	Clock Stop Request, not supported by M_TTCAN use CTL.STOP_REQ at the group level instead. 0= No clock stop is requested 1= Clock stop requested. When clock stop is requested, first INIT and then CSA will be set after all pending transfer requests have been completed and the CAN bus reached idle.
5	MON_	RW	RW	0	Bus Monitoring Mode Bit MON can only be set by the Host when both CCE and INIT are set to '1'. The bit can be reset by the Host at any time. 0= Bus Monitoring Mode is disabled 1= Bus Monitoring Mode is enabled

Bits	Name	SW	HW	Default or Enum	Description
6	DAR	RW	RW	0	Disable Automatic Retransmission 0= Automatic retransmission of messages not transmitted successfully enabled 1= Automatic retransmission disabled
7	TEST	RW	RW	0	Test Mode Enable 0= Normal operation, register TEST holds reset values 1= Test Mode, write access to register TEST enabled
8	FDOE	RW	RW	0	FD Operation Enable 0= FD operation disabled 1= FD operation enabled
9	BRSE	RW	RW	0	Bit Rate Switch Enable 0= Bit rate switching for transmissions disabled 1= Bit rate switching for transmissions enabled
12	PXHD	RW	RW	0	Protocol Exception Handling Disable 0= Protocol exception handling enabled 1= Protocol exception handling disabled
13	EFBI	RW	RW	0	Edge Filtering during Bus Integration 0= Edge filtering disabled 1= Two consecutive dominant tq required to detect an edge for hard synchronization
14	TXP	RW	RW	0	Transmit Pause If this bit is set, the M_TTCAN pauses for two CAN bit times before starting the next transmission after itself has successfully transmitted a frame (see Section 3.5). 0= Transmit pause disabled 1= Transmit pause enabled
15	NISO	RW	RW	0	Non ISO Operation If this bit is set, the M_TTCAN uses the CAN FD frame format as specified by the Bosch CAN FD Specification V1.0. 0= CAN FD frame format according to ISO 11898-1:2015 1= CAN FD frame format according to Bosch CAN FD Specification V1.0 addressing the non-ISO CAN FD

2.3.9.6.7 CANFD_CH_NBTP

Description: Nominal Bit Timing & Prescaler Register
Address: 0x4052001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment: Protected Write. With a CAN clock (m_can_cclk) of 8 MHz, the reset value of 0x06000A03 configures the M_CAN for a bit rate of 500 Kbit/s.
Default: 0x6000A03

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	NTSEG2 [6:0]						
Bits	15	14	13	12	11	10	9	8
Name	NTSEG1 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	NBRP [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	NSJW [31:25]							NBRP [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	NTSEG2	RW	RW	3	Nominal Time segment after sample point 0x01-0x7F Valid values are 1 to 127. The actual interpretation by the hardware of this value is such that one more than the programmed value is used.
8:15	NTSEG1	RW	RW	10	Nominal Time segment before sample point 0x01-0xFF Valid values are 1 to 255. The actual interpretation by the hardware of this value is such that one more than the programmed value is used.
16:24	NBRP	RW	RW	0	Nominal Bit Rate Prescaler 0x000-0x1FF The value by which the oscillator frequency is divided for generating the bit time quanta. The bit time is built up from a multiple of this quanta. Valid values for the Bit Rate Prescaler are 0 to 511. The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.
25:31	NSJW	RW	RW	3	Nominal (Re)Synchronization Jump Width 0x00-0x7F Valid values are 0 to 127. The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.

2.3.9.6.8 CANFD_CH_TSCC

Description: Timestamp Counter Configuration
Address: 0x40520020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						TSS [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				TCP [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	TSS	RW	RW	0	Timestamp Select, should always be set to external timestamp counter 00= Timestamp counter value always 0x0000 01= Timestamp counter value incremented according to TCP 10= External timestamp counter value used 11= Same as '00'
16:19	TCP	RW	RW	0	Timestamp Counter Prescaler (still used for TOCC) 0x0-0xF Configures the timestamp and timeout counters time unit in multiples of CAN bit times [1...16]. The actual interpretation by the hardware of this value is such that one more than the value programmed here is used.

2.3.9.6.9 CANFD_CH_TSCV

Description: Timestamp Counter Value
Address: 0x40520024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TSC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TSC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TSC	RW	RW	0	Timestamp Counter, not used for M_TTCAN The internal/external Timestamp Counter value is captured on start of frame (both Rx and Tx). When TSCC.TSS = '01', the Timestamp Counter is incremented in multiples of CAN bit times [1...16] depending on the configuration of TSCC.TCP. A wrap around sets interrupt flag IR.TSW. Write access resets the counter to zero. When TSCC.TSS = '10', TSC reflects the external Timestamp Counter value. A write access has no impact.

2.3.9.6.10 CANFD_CH_TOCC

Description: Timeout Counter Configuration
Address: 0x40520028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0xFFFF0000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					TOS [2:1]		ETOC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TOP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TOP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ETOC	RW	RW	0	Enable Timeout Counter 0= Timeout Counter disabled 1= Timeout Counter enabled
1:2	TOS	RW	RW	0	Timeout Select When operating in Continuous mode, a write to TOCV presets the counter to the value configured by TOCC.TOP and continues down-counting. When the Timeout Counter is controlled by one of the FIFOs, an empty FIFO presets the counter to the value configured by TOCC.TOP. Down-counting is started when the first FIFO element is stored. 00= Continuous operation 01= Timeout controlled by Tx Event FIFO 10= Timeout controlled by Rx FIFO 0 11= Timeout controlled by Rx FIFO 1
16:31	TOP	RW	RW	65535	Timeout Period Start value of the Timeout Counter (down-counter). Configures the Timeout Period.

2.3.9.6.11 CANFD_CH_TOCV

Description: Timeout Counter Value
Address: 0x4052002C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TOC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TOC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TOC	RW	RW	65535	Timeout Counter The Timeout Counter is decremented in multiples of CAN bit times [1...16] depending on the configuration of TSCC.TCP. When decremented to zero, interrupt flag IR.TOO is set and the Timeout Counter is stopped. Start and reset/restart conditions are configured via TOCC.TOS.

2.3.9.6.12 CANFD_CH_ECR

Description: Error Counter Register
Address: 0x40520040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: Read side effect, except if read from debug host
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RP [15:15]	REC [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	CEL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TEC	R	R	0	Transmit Error Counter Actual state of the Transmit Error Counter, values between 0 and 255
8:14	REC	R	R	0	Receive Error Counter Actual state of the Receive Error Counter, values between 0 and 127
15	RP	R	R	0	Receive Error Passive 0= The Receive Error Counter is below the error passive level of 128 1= The Receive Error Counter has reached the error passive level of 128
16:23	CEL	R	R	0	CAN Error Logging The counter is incremented each time when a CAN protocol error causes the Transmit Error Counter or the Receive Error Counter to be incremented. It is reset by read access to CEL. The counter stops at 0xFF; the next increment of TEC or REC sets interrupt flag IR.ELO.

2.3.9.6.13 CANFD_CH_PSR

Description: Protocol Status Register
Address: 0x40520044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: Read side effect, except if read from debug host
Default: 0x707

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BO [7:7]	EW [6:6]	EP [5:5]	ACT [4:3]		LEC [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	PXE [14:14]	RFDF [13:13]	RBRS [12:12]	RESI [11:11]	DLEC [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	TDCV [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	LEC	R	R	7	Last Error Code, Set on Read0 The LEC indicates the type of the last error to occur on the CAN bus. This field will be cleared to '0' when a message has been transferred (reception or transmission) without error. 0= No Error: No error occurred since LEC has been reset by successful reception or transmission. 1= Stuff Error: More than 5 equal bits in a sequence have occurred in a part of a received message where this is not allowed. 2= Form Error: A fixed format part of a received frame has the wrong format. 3= AckError: The message transmitted by the M_TTCAN was not acknowledged by another node. 4= Bit1Error: During the transmission of a message (with the exception of the arbitration field), the device wanted to send a recessive level (bit of logical value '1'), but the monitored bus value was dominant. 5= Bit0Error: During the transmission of a message (or acknowledge bit, or active error flag, or overload flag), the device wanted to send a dominant level (data or identifier bit logical value 0'), but the monitored bus value was recessive. During Bus_Off recovery this status is set each time a sequence of 11 recessive bits has been monitored. This enables the CPU to monitor the proceeding of the Bus_Off recovery sequence (indicating the bus is not stuck at dominant or continuously disturbed). 6= CRCErrror: The CRC check sum of a received message was incorrect. The CRC of an incoming message does not match with the CRC calculated from the received data. 7= NoChange: Any read access to the Protocol Status Register re-initializes the LEC to '7'. When the LEC shows the value '7', no CAN bus event was detected since the last CPU read access to the Protocol Status Register.
3:4	ACT	R	R	0	Activity Monitors the module's CAN communication state. 00= Synchronizing - node is synchronizing on CAN communication 01= Idle - node is neither receiver nor transmitter 10= Receiver - node is operating as receiver 11= Transmitter - node is operating as transmitter
5	EP	R	R	0	Error Passive 0= The M_CAN is in the Error_Active state. It normally takes part in bus communication and sends an active error flag when an error has been detected 1= The M_CAN is in the Error_Passive state
6	EW	R	R	0	Warning Status 0= Both error counters are below the Error_Warning limit of 96 1= At least one of error counter has reached the Error_Warning limit of 96
7	BO	R	R	0	Bus_Off Status 0= The M_CAN is not Bus_Off 1= The M_CAN is in Bus_Off state

Bits	Name	SW	HW	Default or Enum	Description
8:10	DLEC	R	R	7	Data Phase Last Error Code , Set on Read Type of last error that occurred in the data phase of a CAN FD format frame with its BRS flag set. Coding is the same as for LEC. This field will be cleared to zero when a CAN FD format frame with its BRS flag set has been transferred (reception or transmission) without error.
11	RESI	R	R	0	ESI flag of last received CAN FD Message , Reset on Read This bit is set together with RFDF, independent of acceptance filtering. 0= Last received CAN FD message did not have its ESI flag set 1= Last received CAN FD message had its ESI flag set
12	RBRS	R	R	0	BRS flag of last received CAN FD Message , Reset on Read This bit is set together with RFDF, independent of acceptance filtering. 0= Last received CAN FD message did not have its BRS flag set 1= Last received CAN FD message had its BRS flag set
13	RFDF	R	R	0	Received a CAN FD Message , Reset on Read This bit is set independent of acceptance filtering. 0= Since this bit was reset by the CPU, no CAN FD message has been received 1= Message in CAN FD format with FDF flag set has been received
14	PXE	R	R	0	Protocol Exception Event , Reset on Read 0= No protocol exception event occurred since last read access 1= Protocol exception event occurred
16:22	TDCV	R	R	0	Transmitter Delay Compensation Value 0x00-0x7F Position of the secondary sample point, defined by the sum of the measured delay from m_can_tx to m_can_rx and TDCR.TDCO. The SSP position is, in the data phase, the number of mtq between the start of the transmitted bit and the secondary sample point. Valid values are 0 to 127 mtq.

2.3.9.6.14 CANFD_CH_TDCR

Description: Transmitter Delay Compensation Register
Address: 0x40520048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	TDCF [6:0]						

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	TDCO [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	TDCF	RW	RW	0	Transmitter Delay Compensation Filter Window Length 0x00-0x7F Defines the minimum value for the SSP position, dominant edges on m_ttcn_rx that would result in an earlier SSP position are ignored for transmitter delay measurement. The feature is enabled when TDCF is configured to a value greater than TDCO. Valid values are 0 to 127 mtq
8:14	TDCO	RW	RW	0	Transmitter Delay Compensation Offset 0x00-0x7F Offset value defining the distance between the measured delay from m_ttcn_tx to m_ttcn_rx and the secondary sample point. Valid values are 0 to 127 mtq.

2.3.9.6.15 CANFD_CH_IR

Description: Interrupt Register
Address: 0x40520050
Offset: 0x50
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RF1L_ [7:7]	RF1F [6:6]	RF1W [5:5]	RF1N [4:4]	RF0L_ [3:3]	RF0F [2:2]	RF0W [1:1]	RF0N [0:0]

Bits	15	14	13	12	11	10	9	8
Name	TEFL_ [15:15]	TEFF [14:14]	TEFW [13:13]	TEFN [12:12]	TFE [11:11]	TCF [10:10]	TC [9:9]	HPM [8:8]

Bits	23	22	21	20	19	18	17	16
Name	EP_ [23:23]	ELO [22:22]	BEU [21:21]	BEC [20:20]	DRX [19:19]	TOO [18:18]	MRAF [17:17]	TSW [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		ARA [29:29]	PED [28:28]	PEA [27:27]	WDI [26:26]	BO_ [25:25]	EW_ [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RF0N	RW1C	RW1C	0	Rx FIFO 0 New Message 0= No new message written to Rx FIFO 0 1= New message written to Rx FIFO 0
1	RF0W	RW1C	RW1C	0	Rx FIFO 0 Watermark Reached 0= Rx FIFO 0 fill level below watermark 1= Rx FIFO 0 fill level reached watermark
2	RF0F	RW1C	RW1C	0	Rx FIFO 0 Full 0= Rx FIFO 0 not full 1= Rx FIFO 0 full
3	RF0L_	RW1C	RW1C	0	Rx FIFO 0 Message Lost 0= No Rx FIFO 0 message lost 1= Rx FIFO 0 message lost, also set after write attempt to Rx FIFO 0 of size zero
4	RF1N	RW1C	RW1C	0	Rx FIFO 1 New Message 0= No new message written to Rx FIFO 1 1= New message written to Rx FIFO 1
5	RF1W	RW1C	RW1C	0	Rx FIFO 1 Watermark Reached 0= Rx FIFO 1 fill level below watermark 1= Rx FIFO 1 fill level reached watermark
6	RF1F	RW1C	RW1C	0	Rx FIFO 1 Full 0= Rx FIFO 1 not full 1= Rx FIFO 1 full
7	RF1L_	RW1C	RW1C	0	Rx FIFO 1 Message Lost 0= No Rx FIFO 1 message lost 1= Rx FIFO 1 message lost, also set after write attempt to Rx FIFO 1 of size zero
8	HPM	RW1C	RW1C	0	High Priority Message 0= No high priority message received 1= High priority message received
9	TC	RW1C	RW1C	0	Transmission Completed 0= No transmission completed 1= Transmission completed

Bits	Name	SW	HW	Default or Enum	Description
10	TCF	RW1C	RW1C	0	Transmission Cancellation Finished 0= No transmission cancellation finished 1= Transmission cancellation finished
11	TFE	RW1C	RW1C	0	Tx FIFO Empty 0= Tx FIFO non-empty 1= Tx FIFO empty
12	TEFN	RW1C	RW1C	0	Tx Event FIFO New Entry 0= Tx Event FIFO unchanged 1= Tx Handler wrote Tx Event FIFO element
13	TEFW	RW1C	RW1C	0	Tx Event FIFO Watermark Reached 0= Tx Event FIFO fill level below watermark 1= Tx Event FIFO fill level reached watermark
14	TEFF	RW1C	RW1C	0	Tx Event FIFO Full 0= Tx Event FIFO not full 1= Tx Event FIFO full
15	TEFL_	RW1C	RW1C	0	Tx Event FIFO Element Lost 0= No Tx Event FIFO element lost 1= Tx Event FIFO element lost, also set after write attempt to Tx Event FIFO of size zero
16	TSW	RW1C	RW1C	0	Timestamp Wraparound 0= No timestamp counter wrap-around 1= Timestamp counter wrapped around
17	MRAF	RW1C	RW1C	0	Message RAM Access Failure The flag is set, when the Rx Handler - has not completed acceptance filtering or storage of an accepted message until the arbitration field of the following message has been received. In this case acceptance filtering or message storage is aborted and the Rx Handler starts processing of the following message. - was not able to write a message to the Message RAM. In this case message storage is aborted. In both cases the FIFO put index is not updated resp. the New Data flag for a dedicated Rx Buffer is not set, a partly stored message is overwritten when the next message is stored to this location. The flag is also set when the Tx Handler was not able to read a message from the Message RAM in time. In this case message transmission is aborted. In case of a Tx Handler access failure the M_TTCAN is switched into Restricted Operation Mode (see Section 3.1.5). To leave Restricted Operation Mode, the Host CPU has to reset CCCR.ASM. 0= No Message RAM access failure occurred 1= Message RAM access failure occurred
18	TOO	RW1C	RW1C	0	Timeout Occurred 0= No timeout 1= Timeout reached
19	DRX	RW1C	RW1C	0	Message stored to Dedicated Rx Buffer The flag is set whenever a received message has been stored into a dedicated Rx Buffer. 0= No Rx Buffer updated 1= At least one received message stored into a Rx Buffer

Bits	Name	SW	HW	Default or Enum	Description
20	BEC	RW1C	RW1C	0	M_TTCAN reports correctable ECC fault to the generic fault structure, this bit always reads as 0. Bit Error Corrected Message RAM bit error detected and corrected. Controlled by input signal m_ttcn_aeim_berr[0] generated by an optional external parity / ECC logic attached to the Message RAM. 0= No bit error detected when reading from Message RAM 1= Bit error detected and corrected (e.g. ECC)
21	BEU	RW1C	RW1C	0	Bit Error Uncorrected Message RAM bit error detected, uncorrected. Controlled by input signal m_ttcn_aeim_berr[1] generated by an optional external parity / ECC logic attached to the Message RAM. An uncorrected Message RAM bit error sets CCCR.INIT to '1'. This is done to avoid transmission of corrupted data. 0= No bit error detected when reading from Message RAM 1= Bit error detected, uncorrected (e.g. parity logic)
22	ELO	RW1C	RW1C	0	Error Logging Overflow 0= CAN Error Logging Counter did not overflow 1= Overflow of CAN Error Logging Counter occurred
23	EP_	RW1C	RW1C	0	Error Passive 0= Error_Passive status unchanged 1= Error_Passive status changed
24	EW_	RW1C	RW1C	0	Warning Status 0= Error_Warning status unchanged 1= Error_Warning status changed
25	BO_	RW1C	RW1C	0	Bus_Off Status 0= Bus_Off status unchanged 1= Bus_Off status changed
26	WDI	RW1C	RW1C	0	Watchdog Interrupt 0= No Message RAM Watchdog event occurred 1= Message RAM Watchdog event due to missing READY
27	PEA	RW1C	RW1C	0	Protocol Error in Arbitration Phase (Nominal Bit Time is used) 0= No protocol error in arbitration phase 1= Protocol error in arbitration phase detected (PSR.LEC != 0,7)
28	PED	RW1C	RW1C	0	Protocol Error in Data Phase (Data Bit Time is used) 0= No protocol error in data phase 1= Protocol error in data phase detected (PSR.DLEC != 0,7)
29	ARA	RW1C	RW1C	0	Access to Reserved Address 0= No access to reserved address occurred 1= Access to reserved address occurred

2.3.9.6.16 CANFD_CH_IE

Description: Interrupt Enable
Address: 0x40520054
Offset: 0x54
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RF1LE [7:7]	RF1FE [6:6]	RF1WE [5:5]	RF1NE [4:4]	RF0LE [3:3]	RF0FE [2:2]	RF0WE [1:1]	RF0NE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	TEFLE [15:15]	TEFFE [14:14]	TEFWE [13:13]	TEFNE [12:12]	TFEE [11:11]	TCFE [10:10]	TCE [9:9]	HPME [8:8]

Bits	23	22	21	20	19	18	17	16
Name	EPE [23:23]	ELOE [22:22]	BEUE [21:21]	BECE [20:20]	DRXE [19:19]	TOOE [18:18]	MRAFE [17:17]	TSWE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		ARAE [29:29]	PEDE [28:28]	PEAE [27:27]	WDIE [26:26]	BOE [25:25]	EWE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RF0NE	RW	RW	0	Rx FIFO 0 New Message Interrupt Enable
1	RF0WE	RW	RW	0	Rx FIFO 0 Watermark Reached Interrupt Enable
2	RF0FE	RW	RW	0	Rx FIFO 0 Full Interrupt Enable
3	RF0LE	RW	RW	0	Rx FIFO 0 Message Lost Interrupt Enable
4	RF1NE	RW	RW	0	Rx FIFO 1 New Message Interrupt Enable
5	RF1WE	RW	RW	0	Rx FIFO 1 Watermark Reached Interrupt Enable
6	RF1FE	RW	RW	0	Rx FIFO 1 Full Interrupt Enable
7	RF1LE	RW	RW	0	Rx FIFO 1 Message Lost Interrupt Enable
8	HPME	RW	RW	0	High Priority Message Interrupt Enable
9	TCE	RW	RW	0	Transmission Completed Interrupt Enable
10	TCFE	RW	RW	0	Transmission Cancellation Finished Interrupt Enable
11	TFEE	RW	RW	0	Tx FIFO Empty Interrupt Enable
12	TEFNE	RW	RW	0	Tx Event FIDO New Entry Interrupt Enable
13	TEFWE	RW	RW	0	Tx Event FIFO Watermark Reached Interrupt Enable
14	TEFFE	RW	RW	0	Tx Event FIFO Full Interrupt Enable
15	TEFLE	RW	RW	0	Tx Event FIFO Event Lost Interrupt Enable
16	TSWE	RW	RW	0	Timestamp Wraparound Interrupt Enable
17	MRAFE	RW	RW	0	Message RAM Access Failure Interrupt Enable
18	TOOE	RW	RW	0	Timeout Occurred Interrupt Enable
19	DRXE	RW	RW	0	Message stored to Dedicated Rx Buffer Interrupt Enable
20	BECE	RW	RW	0	Bit Error Corrected Interrupt Enable (not used in M_TTCAN)
21	BEUE	RW	RW	0	Bit Error Uncorrected Interrupt Enable
22	ELOE	RW	RW	0	Error Logging Overflow Interrupt Enable
23	EPE	RW	RW	0	Error Passive Interrupt Enable
24	EWE	RW	RW	0	Warning Status Interrupt Enable

Bits	Name	SW	HW	Default or Enum	Description
25	BOE	RW	RW	0	Bus_Off Status Interrupt Enable
26	WDIE	RW	RW	0	Watchdog Interrupt Enable
27	PEAE	RW	RW	0	Protocol Error in Arbitration Phase Enable
28	PEDE	RW	RW	0	Protocol Error in Data Phase Enable
29	ARAE	RW	RW	0	Access to Reserved Address Enable

2.3.9.6.17 CANFD_CH_ILS

Description: Interrupt Line Select

Address: 0x40520058

Offset: 0x58

Retention: Retained

IsDeepSleep: No

Comment: The Interrupt Line Select register assigns an interrupt generated by a specific interrupt flag from the Interrupt Register to one of the two module interrupt lines. For interrupt generation the respective interrupt line has to be enabled via ILE.EINT0 and ILE.EINT1.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RF1LL [7:7]	RF1FL [6:6]	RF1WL [5:5]	RF1NL [4:4]	RF0LL [3:3]	RF0FL [2:2]	RF0WL [1:1]	RF0NL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	TEFLL [15:15]	TEFFL [14:14]	TEFWL [13:13]	TEFNL [12:12]	TFEL [11:11]	TCFL [10:10]	TCL [9:9]	HPML [8:8]

Bits	23	22	21	20	19	18	17	16
Name	EPL [23:23]	ELOL [22:22]	BEUL [21:21]	BECL [20:20]	DRXL [19:19]	TOOL [18:18]	MRAFL [17:17]	TSWL [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		ARAL [29:29]	PEDL [28:28]	PEAL [27:27]	WDIL [26:26]	BOL [25:25]	EWL [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RF0NL	RW	RW	0	Rx FIFO 0 New Message Interrupt Line
1	RF0WL	RW	RW	0	Rx FIFO 0 Watermark Reached Interrupt Line
2	RF0FL	RW	RW	0	Rx FIFO 0 Full Interrupt Line
3	RF0LL	RW	RW	0	Rx FIFO 0 Message Lost Interrupt Line
4	RF1NL	RW	RW	0	Rx FIFO 1 New Message Interrupt Line
5	RF1WL	RW	RW	0	Rx FIFO 1 Watermark Reached Interrupt Line
6	RF1FL	RW	RW	0	Rx FIFO 1 Full Interrupt Line
7	RF1LL	RW	RW	0	Rx FIFO 1 Message Lost Interrupt Line
8	HPML	RW	RW	0	High Priority Message Interrupt Line
9	TCL	RW	RW	0	Transmission Completed Interrupt Line
10	TCFL	RW	RW	0	Transmission Cancellation Finished Interrupt Line
11	TFEL	RW	RW	0	Tx FIFO Empty Interrupt Line
12	TEFNL	RW	RW	0	Tx Event FIFO New Entry Interrupt Line
13	TEFWL	RW	RW	0	Tx Event FIFO Watermark Reached Interrupt Line
14	TEFFL	RW	RW	0	Tx Event FIFO Full Interrupt Line
15	TEFLL	RW	RW	0	Tx Event FIFO Event Lost Interrupt Line
16	TSWL	RW	RW	0	Timestamp Wraparound Interrupt Line
17	MRAFL	RW	RW	0	Message RAM Access Failure Interrupt Line
18	TOOL	RW	RW	0	Timeout Occurred Interrupt Line
19	DRXL	RW	RW	0	Message stored to Dedicated Rx Buffer Interrupt Line
20	BECL	RW	RW	0	Bit Error Corrected Interrupt Line (not used in M_TTCAN)
21	BEUL	RW	RW	0	Bit Error Uncorrected Interrupt Line
22	ELOL	RW	RW	0	Error Logging Overflow Interrupt Line
23	EPL	RW	RW	0	Error Passive Interrupt Line

Bits	Name	SW	HW	Default or Enum	Description
24	EWL	RW	RW	0	Warning Status Interrupt Line
25	BOL	RW	RW	0	Bus_Off Status Interrupt Line
26	WDIL	RW	RW	0	Watchdog Interrupt Line
27	PEAL	RW	RW	0	Protocol Error in Arbitration Phase Line
28	PEDL	RW	RW	0	Protocol Error in Data Phase Line
29	ARAL	RW	RW	0	Access to Reserved Address Line

2.3.9.6.18 CANFD_CH_ILE

Description: Interrupt Line Enable
Address: 0x4052005C
Offset: 0x5C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						EINT1 [1:1]	EINT0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EINT0	RW	RW	0	Enable Interrupt Line 0 0= Interrupt line m_ttcan_int0 disabled 1= Interrupt line m_ttcan_int0 enabled
1	EINT1	RW	RW	0	Enable Interrupt Line 1 0= Interrupt line m_ttcan_int1 disabled 1= Interrupt line m_ttcan_int1 enabled

2.3.9.6.19 CANFD_CH_GFC

Description: Global Filter Configuration
Address: 0x40520080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		ANFS [5:4]		ANFE [3:2]		RRFS [1:1]	RRFE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RRFE	RW	RW	0	Reject Remote Frames Extended 0= Filter remote frames with 29-bit extended IDs 1= Reject all remote frames with 29-bit extended IDs
1	RRFS	RW	RW	0	Reject Remote Frames Standard 0= Filter remote frames with 11-bit standard IDs 1= Reject all remote frames with 11-bit standard IDs
2:3	ANFE	RW	RW	0	Accept Non-matching Frames Extended Defines how received messages with 29-bit IDs that do not match any element of the filter list are treated. 00= Accept in Rx FIFO 0 01= Accept in Rx FIFO 1 10= Reject 11= Reject
4:5	ANFS	RW	RW	0	Accept Non-matching Frames Standard Defines how received messages with 11-bit IDs that do not match any element of the filter list are treated. 00= Accept in Rx FIFO 0 01= Accept in Rx FIFO 1 10= Reject 11= Reject

2.3.9.6.20 CANFD_CH_SIDFC

Description: Standard ID Filter Configuration
Address: 0x40520084
Offset: 0x84
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	FLSSA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LSS [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	FLSSA	RW	RW	0	Filter List Standard Start Address Start address of standard Message ID filter list (32-bit word address, see Figure 2).
16:23	LSS	RW	RW	0	List Size Standard 0= No standard Message ID filter 1-128= Number of standard Message ID filter elements 128= Values greater than 128 are interpreted as 128

2.3.9.6.21 CANFD_CH_XIDFC

Description: Extended ID Filter Configuration
Address: 0x40520088
Offset: 0x88
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	FLESA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	LSE [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	FLESA	RW	RW	0	Filter List Extended Start Address Start address of extended Message ID filter list (32-bit word address, see Figure 2).
16:22	LSE	RW	RW	0	List Size Extended 0= No extended Message ID filter 1-64= Number of extended Message ID filter elements 64= Values greater than 64 are interpreted as 64

2.3.9.6.22 CANFD_CH_XIDAM

Description: Extended ID AND Mask
Address: 0x40520090
Offset: 0x90
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x1FFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EIDM [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	EIDM [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	EIDM [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			EIDM [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:28	EIDM	RW	RW	536870911	Extended ID Mask For acceptance filtering of extended frames the Extended ID AND Mask is ANDed with the Message ID of a received frame. Intended for masking of 29-bit IDs in SAE J1939. With the reset value of all bits set to one the mask is not active.

2.3.9.6.23 CANFD_CH_HPMS

Description: High Priority Message Status
Address: 0x40520094
Offset: 0x94
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MSI [7:6]		BIDX [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	FLST [15:15]	FIDX [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	BIDX	R	R	0	Buffer Index Index of Rx FIFO element to which the message was stored. Only valid when MSI[1] = '1'.
6:7	MSI	R	R	0	Message Storage Indicator 00= No FIFO selected 01= FIFO message lost 10= Message stored in FIFO 0 11= Message stored in FIFO 1
8:14	FIDX	R	R	0	Filter Index Index of matching filter element. Range is 0 to SIDFC.LSS - 1 resp. XIDFC.LSE - 1.
15	FLST	R	R	0	Filter List Indicates the filter list of the matching filter element. 0= Standard Filter List 1= Extended Filter List

2.3.9.6.24 CANFD_CH_NDAT1

Description: New Data 1
Address: 0x40520098
Offset: 0x98
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ND [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ND [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ND [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ND [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ND	RW1C	RW1C	0	New Data The register holds the New Data flags of Rx Buffers 0 to 31. The flags are set when the respective Rx Buffer has been updated from a received frame. The flags remain set until the Host clears them. A flag is cleared by writing a '1' to the corresponding bit position. Writing a '0' has no effect. A hard reset will clear the register. 0= Rx Buffer not updated 1= Rx Buffer updated from new message

2.3.9.6.25 CANFD_CH_NDAT2

Description: New Data 2
Address: 0x4052009C
Offset: 0x9C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ND [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ND [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ND [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ND [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ND	RW1C	RW1C	0	New Data The register holds the New Data flags of Rx Buffers 32 to 63. The flags are set when the respective Rx Buffer has been updated from a received frame. The flags remain set until the Host clears them. A flag is cleared by writing a '1' to the corresponding bit position. Writing a '0' has no effect. A hard reset will clear the register. 0= Rx Buffer not updated 1= Rx Buffer updated from new message

2.3.9.6.26 CANFD_CH_RXF0C

Description: Rx FIFO 0 Configuration
Address: 0x405200A0
Offset: 0xA0
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	F0SA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	F0S [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	F0OM [31:31]	F0WM [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	F0SA	RW	RW	0	Rx FIFO 0 Start Address Start address of Rx FIFO 0 in Message RAM (32-bit word address, see Figure 2).
16:22	F0S	RW	RW	0	Rx FIFO 0 Size 0= No Rx FIFO 0 1-64= Number of Rx FIFO 0 elements 64= Values greater than 64 are interpreted as 64 The Rx FIFO 0 elements are indexed from 0 to F0S-1
24:30	F0WM	RW	RW	0	Rx FIFO 0 Watermark 0= Watermark interrupt disabled 1-64= Level for Rx FIFO 0 watermark interrupt (IR.RF0W) 64= Watermark interrupt disabled
31	F0OM	RW	RW	0	FIFO 0 Operation Mode FIFO 0 can be operated in blocking or in overwrite mode (see Section 3.4.2). 0= FIFO 0 blocking mode 1= FIFO 0 overwrite mode

2.3.9.6.27 CANFD_CH_RXF0S

Description: Rx FIFO 0 Status
Address: 0x405200A4
Offset: 0xA4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]		F0FL [6:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		F0GI [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		F0PI [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						RF0L [25:25]	F0F [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	F0FL	R	R	0	Rx FIFO 0 Fill Level Number of elements stored in Rx FIFO 0, range 0 to 64.
8:13	F0GI	R	R	0	Rx FIFO 0 Get Index Rx FIFO 0 read index pointer, range 0 to 63. This field is updated by the software writing to RxF0A.F0AI
16:21	F0PI	R	R	0	Rx FIFO 0 Put Index Rx FIFO 0 write index pointer, range 0 to 63.
24	F0F	R	R	0	Rx FIFO 0 Full 0= Rx FIFO 0 not full 1= Rx FIFO 0 full
25	RF0L	R	R	0	Rx FIFO 0 Message Lost This bit is a copy of interrupt flag IR.RF0L. When IR.RF0L is reset, this bit is also reset. 0= No Rx FIFO 0 message lost 1= Rx FIFO 0 message lost, also set after write attempt to Rx FIFO 0 of size zero

2.3.9.6.28 CANFD_CH_RXF0A

Description: Rx FIFO 0 Acknowledge
Address: 0x405200A8
Offset: 0xA8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		F0AI [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	F0AI	RW	RW	0	Rx FIFO 0 Acknowledge Index After the Host has read a message or a sequence of messages from Rx FIFO 0 it has to write the buffer index of the last element read from Rx FIFO 0 to F0AI. This will set the Rx FIFO 0 Get Index RXF0S.F0GI to F0AI + 1 and update the FIFO 0 Fill Level RXF0S.F0FL.

2.3.9.6.29 CANFD_CH_RXBC

Description: Rx Buffer Configuration
Address: 0x405200AC
Offset: 0xAC
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	RBSA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	RBSA	RW	RW	0	Rx Buffer Start Address Configures the start address of the Rx Buffers section in the Message RAM (32-bit word address). Also used to reference debug messages A,B,C.

2.3.9.6.30 CANFD_CH_RXF1C

Description: Rx FIFO 1 Configuration
Address: 0x405200B0
Offset: 0xB0
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	F1SA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	F1S [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	F1OM [31:31]	F1WM [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	F1SA	RW	RW	0	Rx FIFO 1 Start Address Start address of Rx FIFO 1 in Message RAM (32-bit word address, see Figure 2).
16:22	F1S	RW	RW	0	Rx FIFO 1 Size 0= No Rx FIFO 1 1-64= Number of Rx FIFO 1 elements 64= Values greater than 64 are interpreted as 64 The Rx FIFO 1 elements are indexed from 0 to F1S - 1
24:30	F1WM	RW	RW	0	Rx FIFO 1 Watermark 0= Watermark interrupt disabled 1-64= Level for Rx FIFO 1 watermark interrupt (IR.RF1W) 64= Watermark interrupt disabled
31	F1OM	RW	RW	0	FIFO 1 Operation Mode FIFO 1 can be operated in blocking or in overwrite mode (see Section 3.4.2). 0= FIFO 1 blocking mode 1= FIFO 1 overwrite mode

2.3.9.6.31 CANFD_CH_RXF1S

Description: Rx FIFO 1 Status
Address: 0x405200B4
Offset: 0xB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	F1FL [6:0]						

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		F1GI [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		F1PI [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	DMS [31:30]		None [29:26]				RF1L [25:25]	F1F [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	F1FL	R	R	0	Rx FIFO 1 Fill Level Number of elements stored in Rx FIFO 1, range 0 to 64.
8:13	F1GI	R	R	0	Rx FIFO 1 Get Index Rx FIFO 1 read index pointer, range 0 to 63. This field is updated by the software writing to RxF1A.FAI
16:21	F1PI	R	R	0	Rx FIFO 1 Put Index Rx FIFO 1 write index pointer, range 0 to 63.
24	F1F	R	R	0	Rx FIFO 1 Full 0= Rx FIFO 1 not full 1= Rx FIFO 1 full
25	RF1L	R	R	0	Rx FIFO 1 Message Lost This bit is a copy of interrupt flag IR.RF1L. When IR.RF1L is reset, this bit is also reset. 0= No Rx FIFO 1 message lost 1= Rx FIFO 1 message lost, also set after write attempt to Rx FIFO 1 of size zero
30:31	DMS	R	R	0	Debug Message Status 00= Idle state, wait for reception of debug messages, DMA request is cleared 01= Debug message A received 10= Debug messages A, B received 11= Debug messages A, B, C received, DMA request is set

2.3.9.6.32 CANFD_CH_RXF1A

Description: Rx FIFO 1 Acknowledge
Address: 0x405200B8
Offset: 0xB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		F1AI [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	F1AI	RW	RW	0	Rx FIFO 1 Acknowledge Index After the Host has read a message or a sequence of messages from Rx FIFO 1 it has to write the buffer index of the last element read from Rx FIFO 1 to F1AI. This will set the Rx FIFO 1 Get Index RXF1S.F1GI to F1AI + 1 and update the FIFO 1 Fill Level RXF1S.F1FL.

2.3.9.6.33 CANFD_CH_RXESC

Description: Rx Buffer / FIFO Element Size Configuration
Address: 0x405200BC
Offset: 0xBC
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	F1DS [6:4]			None [3:3]	F0DS [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					RBDS [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	F0DS	RW	RW	0	Rx FIFO 0 Data Field Size 000= 8 byte data field 001= 12 byte data field 010= 16 byte data field 011= 20 byte data field 100= 24 byte data field 101= 32 byte data field 110= 48 byte data field 111= 64 byte data field
4:6	F1DS	RW	RW	0	Rx FIFO 1 Data Field Size 000= 8 byte data field 001= 12 byte data field 010= 16 byte data field 011= 20 byte data field 100= 24 byte data field 101= 32 byte data field 110= 48 byte data field 111= 64 byte data field
8:10	RBDS	RW	RW	0	Rx Buffer Data Field Size 000= 8 byte data field 001= 12 byte data field 010= 16 byte data field 011= 20 byte data field 100= 24 byte data field 101= 32 byte data field 110= 48 byte data field 111= 64 byte data field

2.3.9.6.34 CANFD_CH_TXBC

Description: Tx Buffer Configuration
Address: 0x405200C0
Offset: 0xC0
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	TBSA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		NDTB [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	TFQM [30:30]	TFQS [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	TBSA	RW	RW	0	Tx Buffers Start Address Start address of Tx Buffers section in Message RAM (32-bit word address, see Figure 2).
16:21	NDTB	RW	RW	0	Number of Dedicated Transmit Buffers 0= No Dedicated Tx Buffers 1-32= Number of Dedicated Tx Buffers 32= Values greater than 32 are interpreted as 32
24:29	TFQS	RW	RW	0	Transmit FIFO/Queue Size 0= No Tx FIFO/Queue 1-32= Number of Tx Buffers used for Tx FIFO/Queue 32= Values greater than 32 are interpreted as 32
30	TFQM	RW	RW	0	Tx FIFO/Queue Mode 0= Tx FIFO operation 1= Tx Queue operation

2.3.9.6.35 CANFD_CH_TXFQS

Description: Tx FIFO/Queue Status
Address: 0x405200C4
Offset: 0xC4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		TFFL [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			TFGI [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		TFQF [21:21]	TFQPI [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	TFFL	R	R	0	Tx FIFO Free Level Number of consecutive free Tx FIFO elements starting from TFGI, range 0 to 32. Read as zero when Tx Queue operation is configured (TXBC.TFQM = '1')
8:12	TFGI	R	R	0	Tx FIFO Get Index Tx FIFO read index pointer, range 0 to 31. Read as zero when Tx Queue operation is configured (TXBC.TFQM = '1').
16:20	TFQPI	R	R	0	Tx FIFO/Queue Put Index Tx FIFO/Queue write index pointer, range 0 to 31.
21	TFQF	R	R	0	Tx FIFO/Queue Full 0= Tx FIFO/Queue not full 1= Tx FIFO/Queue full

2.3.9.6.36 CANFD_CH_TXESC

Description: Tx Buffer Element Size Configuration
Address: 0x405200C8
Offset: 0xC8
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					TBDS [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	TBDS	RW	RW	0	Tx Buffer Data Field Size 000= 8 byte data field 001= 12 byte data field 010= 16 byte data field 011= 20 byte data field 100= 24 byte data field 101= 32 byte data field 110= 48 byte data field 111= 64 byte data field

2.3.9.6.37 CANFD_CH_TXBRP

Description: Tx Buffer Request Pending
Address: 0x405200CC
Offset: 0xCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TRP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TRP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TRP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TRP	R	R	0	Transmission Request Pending Each Tx Buffer has its own Transmission Request Pending bit. The bits are set via register TXBAR. The bits are reset after a requested transmission has completed or has been cancelled via register TXBCR. TXBRP bits are set only for those Tx Buffers configured via TXBC. After a TXBRP bit has been set, a Tx scan (see Section 3.5, Tx Handling) is started to check for the pending Tx request with the highest priority (Tx Buffer with lowest Message ID). A cancellation request resets the corresponding transmission request pending bit of register TXBRP. In case a transmission has already been started when a cancellation is requested, this is done at the end of the transmission, regardless whether the transmission was successful or not. The cancellation request bits are reset directly after the corresponding TXBRP bit has been reset. After a cancellation has been requested, a finished cancellation is signaled via TXBCF after successful transmission together with the corresponding TXBTO bit when the transmission has not yet been started at the point of cancellation when the transmission has been aborted due to lost arbitration when an error occurred during frame transmission In DAR mode all transmissions are automatically cancelled if they are not successful. The corresponding TXBCF bit is set for all unsuccessful transmissions. 0= No transmission request pending 1= Transmission request pending

2.3.9.6.38 CANFD_CH_TXBAR

Description: Tx Buffer Add Request
Address: 0x405200D0
Offset: 0xD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	AR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	AR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	AR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	AR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	AR	RW	RW	0	Add Request Each Tx Buffer has its own Add Request bit. Writing a '1' will set the corresponding Add Request bit; writing a '0' has no impact. This enables the Host to set transmission requests for multiple Tx Buffers with one write to TXBAR. TXBAR bits are set only for those Tx Buffers configured via TXBC. When no Tx scan is running, the bits are reset immediately, else the bits remain set until the Tx scan process has completed. 0= No transmission request added 1= Transmission requested added

2.3.9.6.39 CANFD_CH_TXBCR

Description: Tx Buffer Cancellation Request
Address: 0x405200D4
Offset: 0xD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CR	RW	RW	0	Cancellation Request Each Tx Buffer has its own Cancellation Request bit. Writing a '1' will set the corresponding Cancellation Request bit; writing a '0' has no impact. This enables the Host to set cancellation requests for multiple Tx Buffers with one write to TXBCR. TXBCR bits are set only for those Tx Buffers configured via TXBC. The bits remain set until the corresponding bit of TXBRP is reset. 0= No cancellation pending 1= Cancellation pending

2.3.9.6.40 CANFD_CH_TXBTO

Description: Tx Buffer Transmission Occurred
Address: 0x405200D8
Offset: 0xD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TO [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TO [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TO [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TO [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TO	R	R	0	Transmission Occurred Each Tx Buffer has its own Transmission Occurred bit. The bits are set when the corresponding TXBRP bit is cleared after a successful transmission. The bits are reset when a new transmission is requested by writing a '1' to the corresponding bit of register TXBAR. 0= No transmission occurred 1= Transmission occurred

2.3.9.6.41 CANFD_CH_TXBCF

Description: Tx Buffer Cancellation Finished
Address: 0x405200DC
Offset: 0xDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CF [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CF [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CF [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CF [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CF	R	R	0	Cancellation Finished Each Tx Buffer has its own Cancellation Finished bit. The bits are set when the corresponding TXBRP bit is cleared after a cancellation was requested via TXBCR. In case the corresponding TXBRP bit was not set at the point of cancellation, CF is set immediately. The bits are reset when a new transmission is requested by writing a '1' to the corresponding bit of register TXBAR. 0= No transmit buffer cancellation 1= Transmit buffer cancellation finished

2.3.9.6.42 CANFD_CH_TXBTIE

Description: Tx Buffer Transmission Interrupt Enable
Address: 0x405200E0
Offset: 0xE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TIE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIE	RW	RW	0	Transmission Interrupt Enable Each Tx Buffer has its own Transmission Interrupt Enable bit. 0= Transmission interrupt disabled 1= Transmission interrupt enable

2.3.9.6.43 CANFD_CH_TXBCIE

Description: Tx Buffer Cancellation Finished Interrupt Enable
Address: 0x405200E4
Offset: 0xE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CFIE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CFIE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CFIE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CFIE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CFIE	RW	RW	0	Cancellation Finished Interrupt Enable Each Tx Buffer has its own Cancellation Finished Interrupt Enable bit. 0= Cancellation finished interrupt disabled 1= Cancellation finished interrupt enabled

2.3.9.6.44 CANFD_CH_TXEFC

Description: Tx Event FIFO Configuration
Address: 0x405200F0
Offset: 0xF0
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	EFSA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		EFS [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		EFWM [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	EFSA	RW	RW	0	Event FIFO Start Address Start address of Tx Event FIFO in Message RAM (32-bit word address, see Figure 2).
16:21	EFS	RW	RW	0	Event FIFO Size 0= Tx Event FIFO disabled 1-32= Number of Tx Event FIFO elements 32= Values greater than 32 are interpreted as 32 The Tx Event FIFO elements are indexed from 0 to EFS-1
24:29	EFWM	RW	RW	0	Event FIFO Watermark 0= Watermark interrupt disabled 1-32= Level for Tx Event FIFO watermark interrupt (IR.TEFW) 32= Watermark interrupt disabled

2.3.9.6.45 CANFD_CH_TXEFS

Description: Tx Event FIFO Status
Address: 0x405200F4
Offset: 0xF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		EFFL [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			EFGI [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			EFPI [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						TEFL [25:25]	EFF [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	EFFL	R	R	0	Event FIFO Fill Level Number of elements stored in Tx Event FIFO, range 0 to 32.
8:12	EFGI	R	R	0	Event FIFO Get Index Tx Event FIFO read index pointer, range 0 to 31.
16:20	EFPI	R	R	0	Event FIFO Put Index Tx Event FIFO write index pointer, range 0 to 31.
24	EFF	R	R	0	Event FIFO Full 0= Tx Event FIFO not full 1= Tx Event FIFO full
25	TEFL	R	R	0	Tx Event FIFO Element Lost This bit is a copy of interrupt flag IR.TEFL. When IR.TEFL is reset, this bit is also reset. 0= No Tx Event FIFO element lost 1= Tx Event FIFO element lost, also set after write attempt to Tx Event FIFO of size zero.

2.3.9.6.46 CANFD_CH_TXEFA

Description: Tx Event FIFO Acknowledge
Address: 0x405200F8
Offset: 0xF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			EFAI [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	EFAI	RW	RW	0	Event FIFO Acknowledge Index After the Host has read an element or a sequence of elements from the Tx Event FIFO it has to write the index of the last element read from Tx Event FIFO to EFAI. This will set the Tx Event FIFO Get Index TXEFS.EFGI to EFAI + 1 and update the Event FIFO Fill Level TXEFS.EFFL.

2.3.9.6.47 CANFD_CH_TTTMC

Description: TT Trigger Memory Configuration
Address: 0x40520100
Offset: 0x100
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	TMSA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	TME [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:15	TMSA	RW	RW	0	Trigger Memory Start Address Start address of Trigger Memory in Message RAM (32-bit word address, see Figure 2).
16:22	TME	RW	RW	0	Trigger Memory Elements 0= No Trigger Memory 1-64= Number of Trigger Memory elements 64= Values greater than 64 are interpreted as 64

2.3.9.6.48 CANFD_CH_TTRMC

Description: TT Reference Message Configuration
Address: 0x40520104
Offset: 0x104
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RID [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	RID [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	RID [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	RMPS [31:31]	XTD [30:30]	None [29:29]	RID [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:28	RID	RW	RW	0	Reference Identifier Identifier transmitted with reference message and used for reference message filtering. Standard or extended reference identifier depending on bit XTD. A standard identifier has to be written to ID[28:18].
30	XTD	RW	RW	0	Extended Identifier 0= 11-bit standard identifier 1= 29-bit extended identifier
31	RMPS	RW	RW	0	Reference Message Payload Select Ignored in case of time slaves. 0= Reference message has no additional payload 1= The following elements are taken from Tx Buffer 0: Message Marker MM, Event FIFO Control EFC, Data Length Code DLC, Data Bytes DB Level 1: bytes 2-8, Level 0,2: bytes 5-8)

2.3.9.6.49 CANFD_CH_TTOCF

Description: TT Operation Configuration
Address: 0x40520108
Offset: 0x108
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x10000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LDSDL [7:5]			TM [4:4]	GEN [3:3]	None [2:2]	OM [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	EECS [15:15]	IRTO [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	AWL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:27]					EVTP [26:26]	ECC [25:25]	EGTF [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	OM	RW	RW	0	Operation Mode 00= Event-driven CAN communication, default 01= TTCAN level 1 10= TTCAN level 2 11= TTCAN level 0
3	GEN	RW	RW	0	Gap Enable 0= Strictly time-triggered operation 1= External event-synchronized time-triggered operation
4	TM	RW	RW	0	Time Master 0= Time Master function disabled 1= Potential Time Master
5:7	LDSDL	RW	RW	0	LD of Synchronization Deviation Limit The Synchronization Deviation Limit SDL is configured by its dual logarithm LDSDL with $SDL = 2(LDSDL + 5)$. It should not exceed the clock tolerance given by the CAN bit timing configuration. 0x0-7 LD of Synchronization Deviation Limit ($SDL \leq 32 \dots 4096$)
8:14	IRTO	RW	RW	0	Initial Reference Trigger Offset 0x00-7F Positive offset, range from 0 to 127
15	EECS	RW	RW	0	Enable External Clock Synchronization If enabled, TUR configuration (TURCF.NCL only) may be updated during TTCAN operation. 0= External clock synchronization in TTCAN Level 0,2 disabled 1= External clock synchronization in TTCAN Level 0,2 enabled

Bits	Name	SW	HW	Default or Enum	Description
16:23	AWL	RW	RW	1	Application Watchdog Limit The application watchdog can be disabled by programming AWL to 0x00. 0x00-FF Maximum time after which the application has to serve the application watchdog. The application watchdog is incremented once each 256 NTUs.
24	EGTF	RW	RW	0	Enable Global Time Filtering 0= Global time filtering in TTCAN Level 0,2 is disabled 1= Global time filtering in TTCAN Level 0,2 is enabled
25	ECC	RW	RW	0	Enable Clock Calibration 0= Automatic clock calibration in TTCAN Level 0,2 is disabled 1= Automatic clock calibration in TTCAN Level 0,2 is enabled
26	EVTP	RW	RW	0	Event Trigger Polarity 0= Rising edge trigger 1= Falling edge trigger

2.3.9.6.50 CANFD_CH_TTLM

Description: TT Matrix Limits
Address: 0x4052010C
Offset: 0x10C
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CSS [7:6]		CCM [5:0]					
Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				TXEW [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	ENTT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				ENTT [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	CCM	RW	RW	0	Cycle Count Max 0x00 1 Basic Cycle per Matrix Cycle 0x01 2 Basic Cycles per Matrix Cycle 0x03 4 Basic Cycles per Matrix Cycle 0x07 8 Basic Cycles per Matrix Cycle 0x0F 16 Basic Cycles per Matrix Cycle 0x1F 32 Basic Cycles per Matrix Cycle 0x3F 64 Basic Cycles per Matrix Cycle others Reserved
6:7	CSS	RW	RW	0	Cycle Start Synchronization Enables sync pulse output at pin m_ttcan_soc. 00= No sync pulse 01= Sync pulse at start of basic cycle 10= Sync pulse at start of matrix cycle 11= Reserved
8:11	TXEW	RW	RW	0	Tx Enable Window 0x0-F Length of Tx enable window, 1-16 NTU cycles
16:27	ENTT	RW	RW	0	Expected Number of Tx Triggers 0x000-FFF Expected number of Tx Triggers in one Matrix Cycle

2.3.9.6.51 CANFD_CH_TURCF

Description: TUR Configuration
Address: 0x40520110
Offset: 0x110
Retention: Retained
IsDeepSleep: No
Comment: Protected Write.
Default: 0x10000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NCL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	NCL [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ELT [31:31]	None [30:30]	DC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	NCL	RW	RW	0	Numerator Configuration Low Write access to the TUR Numerator Configuration Low is only possible during configuration with TURCF.ELT = '0' or if TTOCF.EECS (external clock synchronization enabled) is set. When a new value for NCL is written outside TT Configuration Mode, the new value takes effect when TTOST.WECS is cleared to '0'. NCL is locked TTOST.WECS is '1'. 0x0000-FFFF Numerator Configuration Low
16:29	DC	RW	RW	4096	Denominator Configuration 0x0000 Illegal value 0x0001-3FFF Denominator Configuration
31	ELT	RW	RW	0	Enable Local Time 0= Local time is stopped, default 1= Local time is enabled

2.3.9.6.52 CANFD_CH_TTOCN

Description: TT Operation Control
Address: 0x40520114
Offset: 0x114
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TMC [7:6]		RTIE [5:5]	SWS [4:3]		SWP [2:2]	ECS [1:1]	SGT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	LCKC [15:15]	None [14:14]	ESCN [13:13]	NIG [12:12]	TMG [11:11]	FGP [10:10]	GCS [9:9]	TTIE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SGT	RW	RW	0	Set Global time Writing a '1' to SGT sets TTOST.WGDT if the node is the actual Time Master. SGT is reset after one Host clock period. The global time preset takes effect when the node transmits the next reference message with the Master_Ref_Mark modified by the preset value written to TTGTP.
1	ECS	RW	RW	0	External Clock Synchronization Writing a '1' to ECS sets TTOST.WECS if the node is the actual Time Master. ECS is reset after one Host clock period. The external clock synchronization takes effect at the start of the next basic cycle.
2	SWP	RW	RW	0	Stop Watch Polarity 0= Rising edge trigger 1= Falling edge trigger
3:4	SWS	RW	RW	0	Stop Watch Source 00= Stop Watch disabled 01= Actual value of cycle time is copied to TTCPT.SWV 10= Actual value of local time is copied to TTCPT.SWV 11= Actual value of global time is copied to TTCPT.SWV
5	RTIE	RW	RW	0	Register Time Mark Interrupt Pulse Enable Register time mark interrupts are configured by register TTTMK. A register time mark interrupt pulse with the length of one NTU is generated when the time referenced by TTOCN.TMC (cycle, local, or global) equals TTTMK.TM, independent of the synchronization state. 0= Register Time Mark Interrupt output m_ttcn_rtp disabled 1= Register Time Mark Interrupt output m_ttcn_rtp enabled

Bits	Name	SW	HW	Default or Enum	Description
6:7	TMC	RW	RW	0	Register Time Mark Compare 00= No Register Time Mark Interrupt generated 01= Register Time Mark Interrupt if Time Mark = cycle time 10= Register Time Mark Interrupt if Time Mark = local time 11= Register Time Mark Interrupt if Time Mark = global time
8	TTIE	RW	RW	0	Trigger Time Mark Interrupt Pulse Enable External time mark events are configured by trigger memory element TMEX (see Section 2.4.7). A trigger time mark interrupt pulse is generated when the trigger memory element becomes active, and the M_TTCAN is in synchronization state In_Schedule or In_Gap. 0= Trigger Time Mark Interrupt output m_ttcan_tmp disabled 1= Trigger Time Mark Interrupt output m_ttcan_tmp enabled
9	GCS	RW	RW	0	Gap Control Select 0= Gap control independent from m_ttcan_evt 1= Gap control by input pin m_ttcan_evt
10	FGP	RW	RW	0	Finish Gap Set by the CPU, reset by each reference message 0= No reference message requested 1= Application requested start of reference message
11	TMG	RW	RW	0	Time Mark Gap 0= Reset by each reference message 1= Next reference message started when Register Time Mark interrupt TTIR.RTMI is activated
12	NIG	RW	RW	0	Next is Gap This bit can only be set when the M_TTCAN is the actual Time Master and when it is configured for external event-synchronized time-triggered operation (TTOCF.GEN = '1') 0= No action, reset by reception of any reference message 1= Transmit next reference message with Next_is_Gap = '1'
13	ESCN	RW	RW	0	External Synchronization Control If enabled the M_TTCAN synchronizes its cycle time phase to an external event signaled by a rising edge at pin m_ttcan_evt (see Section 4.11). 0= External synchronization disabled 1= External synchronization enabled
15	LCKC	R	R	0	TT Operation Control Register Locked Set by a write access to register TTOCN. Reset when the updated configuration has been synchronized into the CAN clock domain. 0= Write access to TTOCN enabled 1= Write access to TTOCN locked

2.3.9.6.53 CANFD_CH_TTGTP

Description: TT Global Time Preset
Address: 0x40520118
Offset: 0x118
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CTP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CTP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TP	RW	RW	0	Time Preset TP is write-protected while TTOST.WGTD is set. 0x0000-7FFF Next Master Reference Mark = Master Reference Mark + TP 0x8000 reserved 0x8001-FFFF Next Master Reference Mark = Master Reference Mark - (0x10000 - TP)
16:31	CTP	RW	RW	0	Cycle Time Target Phase CTP is write-protected while TTOCN.ESCN or TTOST.SPL are set (see Section 4.11). 0x0000-FFFF Defines target value of cycle time when a rising edge of m_tcan_evt is expected

2.3.9.6.54 CANFD_CH_TTTMK

Description: TT Time Mark
Address: 0x4052011C
Offset: 0x11C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TM_ [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TM_ [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	TICC [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	LCKM [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TM_	RW	RW	0	Time Mark 0x0000-FFFF Time Mark
16:22	TICC	RW	RW	0	Time Mark Cycle Code Cycle count for which the time mark is valid. 0b000000x valid for all cycles 0b000001c valid every second cycle at cycle count mod2 = c 0b00001cc valid every fourth cycle at cycle count mod4 = cc 0b0001ccc valid every eighth cycle at cycle count mod8 = ccc 0b001cccc valid every sixteenth cycle at cycle count mod16 = cccc 0b01ccccc valid every thirty-second cycle at cycle count mod32 = ccccc 0b1cccccc valid every sixty-fourth cycle at cycle count mod64 = ccccccc
31	LCKM	R	R	0	TT Time Mark Register Locked Always set by a write access to registers TTOCN. Set by write access to register TTTMK when TTOCN.TMC != '00'. Reset when the registers have been synchronized into the CAN clock domain. 0= Write access to TTTMK enabled 1= Write access to TTTMK locked

2.3.9.6.55 CANFD_CH_TTIR

Description: TT Interrupt Register
Address: 0x40520120
Offset: 0x120
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	GTW [7:7]	SWE [6:6]	TTMI [5:5]	RTMI [4:4]	SOG [3:3]	CSM_ [2:2]	SMC [1:1]	SBC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	IWT [15:15]	ELC [14:14]	SE2 [13:13]	SE1 [12:12]	TXO [11:11]	TXU [10:10]	GTE [9:9]	GTD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					CER [18:18]	AW [17:17]	WT [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SBC	RW1C	RW1C	0	Start of Basic Cycle 0= No Basic Cycle started since bit has been reset 1= Basic Cycle started
1	SMC	RW1C	RW1C	0	Start of Matrix Cycle 0= No Matrix Cycle started since bit has been reset 1= Matrix Cycle started
2	CSM_	RW1C	RW1C	0	Change of Synchronization Mode 0= No change in master to slave relation or schedule synchronization 1= Master to slave relation or schedule synchronization changed, also set when TTOST.SPL is reset
3	SOG	RW1C	RW1C	0	Start of Gap 0= No reference message seen with Next_is_Gap bit set 1= Reference message with Next_is_Gap bit set becomes valid
4	RTMI	RW1C	RW1C	0	Register Time Mark Interrupt Set when time referenced by TTOCN.TMC (cycle, local, or global) equals TTTMK.TM, independent of the synchronization state. 0= Time mark not reached 1= Time mark reached
5	TTMI	RW1C	RW1C	0	Trigger Time Mark Event Internal Internal time mark events are configured by trigger memory element TMIN (see Section 2.4.7). Set when the trigger memory element becomes active, and the M_TTCAN is in synchronization state In_Gap or In_Schedule. 0= Time mark not reached 1= Time mark reached (Level 0: cycle time TTOCF.IRTO * 0x200)

Bits	Name	SW	HW	Default or Enum	Description
6	SWE	RW1C	RW1C	0	Stop Watch Event 0= No rising/falling edge at stop watch trigger pin m_ttcn_swt detected 1= Rising/falling edge at stop watch trigger pin m_ttcn_swt detected
7	GTW	RW1C	RW1C	0	Global Time Wrap 0= No global time wrap occurred 1= Global time wrap from 0xFFFF to 0x0000 occurred
8	GTD	RW1C	RW1C	0	Global Time Discontinuity 0= No discontinuity of global time 1= Discontinuity of global time
9	GTE	RW1C	RW1C	0	Global Time Error Synchronization deviation SD exceeds limit specified by TTOCF.LDSDL, TTCAN Level 0,2 only. 0= Synchronization deviation within limit 1= Synchronization deviation exceeded limit
10	TXU	RW1C	RW1C	0	Tx Count Underflow 0= Number of Tx Trigger as expected 1= Less Tx trigger than expected in one matrix cycle
11	TXO	RW1C	RW1C	0	Tx Count Overflow 0= Number of Tx Trigger as expected 1= More Tx trigger than expected in one matrix cycle
12	SE1	RW1C	RW1C	0	Scheduling Error 1 0= No scheduling error 1 1= Scheduling error 1 occurred
13	SE2	RW1C	RW1C	0	Scheduling Error 2 0= No scheduling error 2 1= Scheduling error 2 occurred
14	ELC	RW1C	RW1C	0	Error Level Changed Not set when error level changed during initialization. 0= No change in error level 1= Error level changed
15	IWT	RW1C	RW1C	0	Initialization Watch Trigger The initialization is restarted by resetting IWT. 0= No missing reference message during system startup 1= No system startup due to missing reference message
16	WT	RW1C	RW1C	0	Watch Trigger 0= No missing reference message 1= Missing reference message (Level 0: cycle time 0xFF00)
17	AW	RW1C	RW1C	0	Application Watchdog 0= Application watchdog served in time 1= Application watchdog not served in time
18	CER	RW1C	RW1C	0	Configuration Error Trigger out of order. 0= No error found in trigger list 1= Error found in trigger list

2.3.9.6.56 CANFD_CH_TTIE

Description: TT Interrupt Enable
Address: 0x40520124
Offset: 0x124
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	GTWE [7:7]	SWEE [6:6]	TTMIE [5:5]	RTMIE [4:4]	SOGIE [3:3]	CSME [2:2]	SMCE [1:1]	SBCE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	IWTE [15:15]	ELCE [14:14]	SE2E [13:13]	SE1E [12:12]	TXOE [11:11]	TXUE [10:10]	GTEE [9:9]	GTDE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					CERE [18:18]	AWE_ [17:17]	WTE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SBCE	RW	RW	0	Start of Basic Cycle Interrupt Enable
1	SMCE	RW	RW	0	Start of Matrix Cycle Interrupt Enable
2	CSME	RW	RW	0	Change of Synchronization Mode Interrupt Enable
3	SOGIE	RW	RW	0	Start of Gap Interrupt Enable
4	RTMIE	RW	RW	0	Register Time Mark Interrupt Enable
5	TTMIE	RW	RW	0	Trigger Time Mark Event Internal Enable
6	SWEE	RW	RW	0	Stop Watch Event Interrupt Enable
7	GTWE	RW	RW	0	Global Time Wrap Interrupt Enable
8	GTDE	RW	RW	0	Global Time Discontinuity Interrupt Enable
9	GTEE	RW	RW	0	Global Time Error Interrupt Enable
10	TXUE	RW	RW	0	Tx Count Underflow Interrupt Enable
11	TXOE	RW	RW	0	Tx Count Overflow Interrupt Enable
12	SE1E	RW	RW	0	Scheduling Error 1 Interrupt Enable
13	SE2E	RW	RW	0	Scheduling Error 2 Interrupt Enable
14	ELCE	RW	RW	0	Change Error Level Interrupt Enable
15	IWTE	RW	RW	0	Initialization Watch Trigger Interrupt Enable
16	WTE	RW	RW	0	Watch Trigger Interrupt Enable
17	AWE_	RW	RW	0	Application Watchdog Interrupt Enable
18	CERE	RW	RW	0	Configuration Error Interrupt Enable

2.3.9.6.57 CANFD_CH_TTILS

Description: TT Interrupt Line Select

Address: 0x40520128

Offset: 0x128

Retention: Retained

IsDeepSleep: No

Comment: The TT Interrupt Line Select register assigns an interrupt generated by a specific interrupt flag from the TT Interrupt Register to one of the two module interrupt lines. For interrupt generation the respective interrupt line has to be enabled via ILE.EINT0 and ILE.EINT1. 0= TT interrupt assigned to interrupt line m_ttcan_int0 1= TT interrupt assigned to interrupt line m_ttcan_int1

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	GTWL [7:7]	SWEL [6:6]	TTMIL [5:5]	RTMIL [4:4]	SOGL [3:3]	CSML [2:2]	SMCL [1:1]	SBCL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	IWTL [15:15]	ELCL [14:14]	SE2L [13:13]	SE1L [12:12]	TXOL [11:11]	TXUL [10:10]	GTEL [9:9]	GTDL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					CERL [18:18]	AWL_ [17:17]	WTL [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SBCL	RW	RW	0	Start of Basic Cycle Interrupt Line
1	SMCL	RW	RW	0	Start of Matrix Cycle Interrupt Line
2	CSML	RW	RW	0	Change of Synchronization Mode Interrupt Line
3	SOGL	RW	RW	0	Start of Gap Interrupt Line
4	RTMIL	RW	RW	0	Register Time Mark Interrupt Line
5	TTMIL	RW	RW	0	Trigger Time Mark Event Internal Line
6	SWEL	RW	RW	0	Stop Watch Event Interrupt Line
7	GTWL	RW	RW	0	Global Time Wrap Interrupt Line
8	GTDL	RW	RW	0	Global Time Discontinuity Interrupt Line
9	GTEL	RW	RW	0	Global Time Error Interrupt Line
10	TXUL	RW	RW	0	Tx Count Underflow Interrupt Line
11	TXOL	RW	RW	0	Tx Count Overflow Interrupt Line
12	SE1L	RW	RW	0	Scheduling Error 1 Interrupt Line
13	SE2L	RW	RW	0	Scheduling Error 2 Interrupt Line
14	ELCL	RW	RW	0	Change Error Level Interrupt Line
15	IWTL	RW	RW	0	Initialization Watch Trigger Interrupt Line
16	WTL	RW	RW	0	Watch Trigger Interrupt Line
17	AWL_	RW	RW	0	Application Watchdog Interrupt Line
18	CERL	RW	RW	0	Configuration Error Interrupt Line

2.3.9.6.58 CANFD_CH_TTOST

Description: TT Operation Status
Address: 0x4052012C
Offset: 0x12C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QCS [7:7]	QGTP [6:6]	SYS [5:4]		MS [3:2]		EL [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	RTO [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	GFI [23:23]	WGTD [22:22]	None [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	SPL [31:31]	WECS [30:30]	AWE [29:29]	WFE [28:28]	GSI [27:27]	TMP [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	EL	R	R	0	Error Level 00= Severity 0 - No Error 01= Severity 1 - Warning 10= Severity 2 - Error 11= Severity 3 - Severe Error
2:3	MS	R	R	0	Master State 00= Master_Off, no master properties relevant 01= Operating as Time Slave 10= Operating as Backup Time Master 11= Operating as current Time Master
4:5	SYS	R	R	0	Synchronization State 00= Out of Synchronization 01= Synchronizing to TTCAN communication 10= Schedule suspended by Gap (In_Gap) 11= Synchronized to schedule (In_Schedule)
6	QGTP	R	R	0	Quality of Global Time Phase Only relevant in TTCAN Level 0 and Level 2, otherwise fixed to '0'. 0= Global time not valid 1= Global time in phase with Time Master
7	QCS	R	R	0	Quality of Clock Speed Only relevant in TTCAN Level 0 and Level 2, otherwise fixed to '1'. 0= Local clock speed not synchronized to Time Master clock speed 1= Synchronization Deviation <= SDL

Bits	Name	SW	HW	Default or Enum	Description
8:15	RTO	R	R	0	Reference Trigger Offset The Reference Trigger Offset value is a signed integer with a range from -127 (0x81) to 127 (0x7F). There is no notification when the lower limit of -127 is reached. In case the M_TTCAN becomes Time Master (MS[1:0] = '11'), the reset of RTO is delayed due to synchronization between Host and CAN clock domain. For time slaves the value configured by TTOCF.IRTO is read. 0x00-FF Actual Reference Trigger offset value
22	WGTD	R	R	0	Wait for Global Time Discontinuity 0= No global time preset pending 1= Node waits for the global time preset to take effect. The bit is reset when the node has transmitted a reference message with Disc_Bit = '1' or after it received a reference message.
23	GFI	R	R	0	Gap Finished Indicator Set when the CPU writes TTOCN.FGP, or by a time mark interrupt if TMG = '1', or via input pin m_ttcn_evt if TTOCN.GCS = '1'. Not set by Ref_Trigger_Gap or when Gap is finished by another node sending a reference message. 0= Reset at the end of each reference message 1= Gap finished by M_TTCAN
24:26	TMP	R	R	0	Time Master Priority 0x0-7 Priority of actual Time Master
27	GSI	R	R	0	Gap Started Indicator 0= No Gap in schedule, reset by each reference message and for all time slaves 1= Gap time after Basic Cycle has started
28	WFE	R	R	0	Wait for Event 0= No Gap announced, reset by a reference message with Next_is_Gap = '0' 1= Reference message with Next_is_Gap = '1' received
29	AWE	R	R	0	Application Watchdog Event The application watchdog is served by reading TTOST. When the watchdog is not served in time, bit AWE is set, all TTCAN communication is stopped, and the M_TTCAN is set into Bus Monitoring Mode. 0= Application Watchdog served in time 1= Failed to serve Application Watchdog in time
30	WECS	R	R	0	Wait for External Clock Synchronization 0= No external clock synchronization pending 1= Node waits for external clock synchronization to take effect. The bit is reset at the start of the next basic cycle.
31	SPL	R	R	0	Schedule Phase Lock The bit is valid only when external synchronization is enabled (TTOCN.ESCN = '1'). In this case it signals that the difference between cycle time configured by TTGTP.CTP and the cycle time at the rising edge at pin m_ttcn_evt is less or equal 9 NTU (see Section 4.11). 0= Phase outside range 1= Phase inside range

2.3.9.6.59 CANFD_CH_TURNA

Description: TUR Numerator Actual
Address: 0x40520130
Offset: 0x130
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NAV [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	NAV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						NAV [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	NAV	R	R	65536	Numerator Actual Value 0x0EFFF reserved 0x0F000-20FFF Actual numerator value 0x21000 reserved

2.3.9.6.60 CANFD_CH_TTLGT

Description: TT Local & Global Time
Address: 0x40520134
Offset: 0x134
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	GT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	GT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	LT	R	R	0	Local Time Non-fractional part of local time, incremented once each local NTU (see Section 4.5). 0x0000-FFFF Local time value of TTCAN node
16:31	GT	R	R	0	Global Time Non-fractional part of the sum of the node's local time and its local offset (see Section 4.5). 0x0000-FFFF Global time value of TTCAN network

2.3.9.6.61 CANFD_CH_TTCTC

Description: TT Cycle Time & Count
Address: 0x40520138
Offset: 0x138
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3F0000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		CC [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	CT	R	R	0	Cycle Time Non-fractional part of the difference of the node's local time and Ref_Mark (see Section 4.5). 0x0000-FFFF Cycle time value of TTCAN Basic Cycle
16:21	CC	R	R	63	Cycle Count 0x00-3F Number of actual Basic Cycle in the System Matrix

2.3.9.6.62 CANFD_CH_TTCPT

Description: TT Capture Time
Address: 0x4052013C
Offset: 0x13C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CCV [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SWV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SWV [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	CCV	R	R	0	Cycle Count Value Cycle count value captured together with SWV. 0x00-3F Captured cycle count value
16:31	SWV	R	R	0	Stop Watch Value On a rising/falling edge (as configured via TTOCN.SWP) at the Stop Watch Trigger pin m_ttcan_swt, when TTOCN.SWS is != '00' and TTIR.SWE is '0', the actual time value as selected by TTOCN.SWS (cycle, local, global) is copied to SWV and TTIR.SWE will be set to '1'. Capturing of the next stop watch value is enabled by resetting TTIR.SWE. 0x0000-FFFF Captured Stop Watch value

2.3.9.6.63 CANFD_CH_TTCSM

Description: TT Cycle Sync Mark
Address: 0x40520140
Offset: 0x140
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CSM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CSM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	CSM	R	R	0	Cycle Sync Mark The Cycle Sync Mark is measured

3 CM0P

Description	Cortex-M0+ specific registers
Base Address	0xE0000000
Size	0x20000000
Slave Num	SYSTEM

3.1 DWT

Register Name	Address	Permission	Description
CM0P_DWT_DWT_CTRL	0xE0001000	FULL	Watchpoint Comparator Configuration
CM0P_DWT_DWT_PCSR	0xE000101C	FULL	Watchpoint Comparator PC Sample
CM0P_DWT_DWT_COMP0	0xE0001020	FULL	Watchpoint Comparator Compare Value
CM0P_DWT_DWT_MASK0	0xE0001024	FULL	Watchpoint Comparator Mask
CM0P_DWT_DWT_FUNCTION0	0xE0001028	FULL	Watchpoint Comparator Function
CM0P_DWT_DWT_COMP1	0xE0001030	FULL	Watchpoint Comparator Compare Value
CM0P_DWT_DWT_MASK1	0xE0001034	FULL	Watchpoint Comparator Mask
CM0P_DWT_DWT_FUNCTION1	0xE0001038	FULL	Watchpoint Comparator Function
CM0P_DWT_DWT_PID4	0xE0001FD0	FULL	Watchpoint Unit CoreSight ROM Table Peripheral ID #4
CM0P_DWT_DWT_PID0	0xE0001FE0	FULL	Watchpoint Unit CoreSight ROM Table Peripheral ID #0
CM0P_DWT_DWT_PID1	0xE0001FE4	FULL	Watchpoint Unit CoreSight ROM Table Peripheral ID #1
CM0P_DWT_DWT_PID2	0xE0001FE8	FULL	Watchpoint Unit CoreSight ROM Table Peripheral ID #2
CM0P_DWT_DWT_PID3	0xE0001FEC	FULL	Watchpoint Unit CoreSight ROM Table Peripheral ID #3
CM0P_DWT_DWT_CID0	0xE0001FF0	FULL	Watchpoint Unit CoreSight ROM Table Component ID #0
CM0P_DWT_DWT_CID1	0xE0001FF4	FULL	Watchpoint Unit CoreSight ROM Table Component ID #1
CM0P_DWT_DWT_CID2	0xE0001FF8	FULL	Watchpoint Unit CoreSight ROM Table Component ID #2
CM0P_DWT_DWT_CID3	0xE0001FFC	FULL	Watchpoint Unit CoreSight ROM Table Component ID #3

3.2 BP

Register Name	Address	Permission	Description
CM0P_BP_BP_CTRL	0xE0002000	FULL	Breakpoint Unit Control
CM0P_BP_BP_COMP0	0xE0002008	FULL	Breakpoint Compare Register
CM0P_BP_BP_COMP1	0xE000200C	FULL	Breakpoint Compare Register
CM0P_BP_BP_COMP2	0xE0002010	FULL	Breakpoint Compare Register
CM0P_BP_BP_COMP3	0xE0002014	FULL	Breakpoint Compare Register
CM0P_BP_BP_PID4	0xE0002FD0	FULL	Breakpoint Unit CoreSight ROM Table Peripheral ID #4
CM0P_BP_BP_PID0	0xE0002FE0	FULL	Breakpoint Unit CoreSight ROM Table Peripheral ID #0
CM0P_BP_BP_PID1	0xE0002FE4	FULL	Breakpoint Unit CoreSight ROM Table Peripheral ID #1
CM0P_BP_BP_PID2	0xE0002FE8	FULL	Breakpoint Unit CoreSight ROM Table Peripheral ID #2
CM0P_BP_BP_PID3	0xE0002FEC	FULL	Breakpoint Unit CoreSight ROM Table Peripheral ID #3
CM0P_BP_BP_CID0	0xE0002FF0	FULL	Breakpoint Unit CoreSight ROM Table Component ID #0
CM0P_BP_BP_CID1	0xE0002FF4	FULL	Breakpoint Unit CoreSight ROM Table Component ID #1
CM0P_BP_BP_CID2	0xE0002FF8	FULL	Breakpoint Unit CoreSight ROM Table Component ID #2
CM0P_BP_BP_CID3	0xE0002FFC	FULL	Breakpoint Unit CoreSight ROM Table Component ID #3

3.3 SCS

Register Name	Address	Permission	Description
CM0P_SCS_SYST_CSR	0xE000E010	FULL	SysTick Control & Status
CM0P_SCS_SYST_RVR	0xE000E014	FULL	SysTick Reload Value
CM0P_SCS_SYST_CVR	0xE000E018	FULL	SysTick Current Value
CM0P_SCS_SYST_CALIB	0xE000E01C	FULL	SysTick Calibration Value
CM0P_SCS_ISER	0xE000E100	FULL	Interrupt Set-Enable Register
CM0P_SCS_ICER	0xE000E180	FULL	Interrupt Clear Enable Register
CM0P_SCS_ISPR	0xE000E200	FULL	Interrupt Set-Pending Register
CM0P_SCS_ICPR	0xE000E280	FULL	Interrupt Clear-Pending Register
CM0P_SCS_IPR0	0xE000E400	FULL	Interrupt Priority Registers
CM0P_SCS_IPR1	0xE000E404	FULL	Interrupt Priority Registers
CM0P_SCS_IPR2	0xE000E408	FULL	Interrupt Priority Registers
CM0P_SCS_IPR3	0xE000E40C	FULL	Interrupt Priority Registers
CM0P_SCS_IPR4	0xE000E410	FULL	Interrupt Priority Registers
CM0P_SCS_IPR5	0xE000E414	FULL	Interrupt Priority Registers
CM0P_SCS_IPR6	0xE000E418	FULL	Interrupt Priority Registers
CM0P_SCS_IPR7	0xE000E41C	FULL	Interrupt Priority Registers
CM0P_SCS_CPUID	0xE000ED00	FULL	CPUID Register
CM0P_SCS_ICSR	0xE000ED04	FULL	Interrupt Control State Register
CM0P_SCS_VTOR	0xE000ED08	FULL	Vector Table Offset Register
CM0P_SCS_AIRCR	0xE000ED0C	FULL	Application Interrupt and Reset Control Register
CM0P_SCS_SCR	0xE000ED10	FULL	System Control Register
CM0P_SCS_CCR	0xE000ED14	FULL	Configuration and Control Register
CM0P_SCS_SHPR2	0xE000ED1C	FULL	System Handler Priority Register 2
CM0P_SCS_SHPR3	0xE000ED20	FULL	System Handler Priority Register 3
CM0P_SCS_SHCSR	0xE000ED24	FULL	System Handler Control and State Register
CM0P_SCS_DFSR	0xE000ED30	FULL	Debug Fault Status Register
CM0P_SCS_MPU_TYPE	0xE000ED90	FULL	MPU Type Register
CM0P_SCS_MPU_CTRL	0xE000ED94	FULL	MPU Control Register
CM0P_SCS_MPU_RNR	0xE000ED98	FULL	MPU Region Number Register
CM0P_SCS_MPU_RBAR	0xE000ED9C	FULL	MPU Region Base Address Register
CM0P_SCS_MPU_RASR	0xE000EDA0	FULL	MPU Region Attribute and Size Register
CM0P_SCS_DHCSR	0xE000EDF0	FULL	Debug Halting Control and Status Register
CM0P_SCS_DCRSR	0xE000EDF4	FULL	Debug Core Register Selector Register
CM0P_SCS_DCRDR	0xE000EDF8	FULL	Debug Core Register Data Register
CM0P_SCS_DEMCR	0xE000EDFC	FULL	Debug Exception and Monitor Control Register
CM0P_SCS_SCS_PID4	0xE000EFD0	FULL	System Control Space ROM Table Peripheral ID #4
CM0P_SCS_SCS_PID0	0xE000EFE0	FULL	System Control Space ROM Table Peripheral ID #0
CM0P_SCS_SCS_PID1	0xE000EFE4	FULL	System Control Space ROM Table Peripheral ID #1
CM0P_SCS_SCS_PID2	0xE000EFE8	FULL	System Control Space ROM Table Peripheral ID #2
CM0P_SCS_SCS_PID3	0xE000EFEC	FULL	System Control Space ROM Table Peripheral ID #3
CM0P_SCS_SCS_CID0	0xE000EFF0	FULL	System Control Space ROM Table Component ID #0
CM0P_SCS_SCS_CID1	0xE000EFF4	FULL	System Control Space ROM Table Component ID #1
CM0P_SCS_SCS_CID2	0xE000EFF8	FULL	System Control Space ROM Table Component ID #2
CM0P_SCS_SCS_CID3	0xE000EFFC	FULL	System Control Space ROM Table Component ID #3

3.4 ROM

Register Name	Address	Permission	Description
CM0P_ROM_ROM_SCS	0xE00FF000	FULL	CM0+ CoreSight ROM Table Peripheral #0
CM0P_ROM_ROM_DWT	0xE00FF004	FULL	CM0+ CoreSight ROM Table Peripheral #1
CM0P_ROM_ROM_BPU	0xE00FF008	FULL	CM0+ CoreSight ROM Table Peripheral #2
CM0P_ROM_ROM_END	0xE00FF00C	FULL	CM0+ CoreSight ROM Table End Marker

Register Name	Address	Permission	Description
CM0P_ROM_ROM_CSMT	0xE00FFFC0	FULL	CM0+ CoreSight ROM Table Memory Type
CM0P_ROM_ROM_PID4	0xE00FFFD0	FULL	CM0+ CoreSight ROM Table Peripheral ID #4
CM0P_ROM_ROM_PID0	0xE00FFFE0	FULL	CM0+ CoreSight ROM Table Peripheral ID #0
CM0P_ROM_ROM_PID1	0xE00FFFE4	FULL	CM0+ CoreSight ROM Table Peripheral ID #1
CM0P_ROM_ROM_PID2	0xE00FFFE8	FULL	CM0+ CoreSight ROM Table Peripheral ID #2
CM0P_ROM_ROM_PID3	0xE00FFFEC	FULL	CM0+ CoreSight ROM Table Peripheral ID #3
CM0P_ROM_ROM_CID0	0xE00FFFF0	FULL	CM0+ CoreSight ROM Table Component ID #0
CM0P_ROM_ROM_CID1	0xE00FFFF4	FULL	CM0+ CoreSight ROM Table Component ID #1
CM0P_ROM_ROM_CID2	0xE00FFFF8	FULL	CM0+ CoreSight ROM Table Component ID #2
CM0P_ROM_ROM_CID3	0xE00FFFFC	FULL	CM0+ CoreSight ROM Table Component ID #3

3.5 ROMTABLE

Register Name	Address	Permission	Description
CM0P_ROMTABLE_ADDR0	0xF0000000	FULL	Link to Cortex M0+ ROM Table.
CM0P_ROMTABLE_ADDR1	0xF0000004	FULL	Link to CoreSight CTI Table.
CM0P_ROMTABLE_ADDR2	0xF0000008	FULL	Link to Cortex M0+ MTB Table.
CM0P_ROMTABLE_DID	0xF0000FCC	FULL	Device Type Identifier register.
CM0P_ROMTABLE_PID4	0xF0000FD0	FULL	Peripheral Identification Register 4.
CM0P_ROMTABLE_PID5	0xF0000FD4	FULL	Peripheral Identification Register 5.
CM0P_ROMTABLE_PID6	0xF0000FD8	FULL	Peripheral Identification Register 6.
CM0P_ROMTABLE_PID7	0xF0000FDC	FULL	Peripheral Identification Register 7.
CM0P_ROMTABLE_PID0	0xF0000FE0	FULL	Peripheral Identification Register 0.
CM0P_ROMTABLE_PID1	0xF0000FE4	FULL	Peripheral Identification Register 1.
CM0P_ROMTABLE_PID2	0xF0000FE8	FULL	Peripheral Identification Register 2.
CM0P_ROMTABLE_PID3	0xF0000FEC	FULL	Peripheral Identification Register 3.
CM0P_ROMTABLE_CID0	0xF0000FF0	FULL	Component Identification Register 0.
CM0P_ROMTABLE_CID1	0xF0000FF4	FULL	Component Identification Register 1.
CM0P_ROMTABLE_CID2	0xF0000FF8	FULL	Component Identification Register 2.
CM0P_ROMTABLE_CID3	0xF0000FFC	FULL	Component Identification Register 3.

3.6 CTI

Register Name	Address	Permission	Description
CM0P_CTI_CTLCONTROL	0xF0002000	FULL	CTI Control Register
CM0P_CTI_CTLINTACK	0xF0002010	FULL	CTI Interrupt Acknowledge Register
CM0P_CTI_CTLAPPSET	0xF0002014	FULL	CTI Application Trigger Set Register
CM0P_CTI_CTLAPPCLEAR	0xF0002018	FULL	CTI Application Trigger Clear Register
CM0P_CTI_CTLAPPULSE	0xF000201C	FULL	CTI Application Pulse Register
CM0P_CTI_CTLINEN0	0xF0002020	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN1	0xF0002024	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN2	0xF0002028	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN3	0xF000202C	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN4	0xF0002030	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN5	0xF0002034	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN6	0xF0002038	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLINEN7	0xF000203C	FULL	CTI Trigger to Channel Enable Registers
CM0P_CTI_CTLIOUTEN0	0xF00020A0	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN1	0xF00020A4	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN2	0xF00020A8	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN3	0xF00020AC	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN4	0xF00020B0	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN5	0xF00020B4	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN6	0xF00020B8	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLIOUTEN7	0xF00020BC	FULL	CTI Channel to Trigger Enable Registers
CM0P_CTI_CTLTRIGINSTATUS	0xF0002130	FULL	CTI Trigger In Status Register
CM0P_CTI_CTLTRIGOUTSTATUS	0xF0002134	FULL	CTI Trigger Out Status Register
CM0P_CTI_CTLCHINSTATUS	0xF0002138	FULL	CTI Channel In Status Register
CM0P_CTI_CTLCHOUTSTATUS	0xF000213C	FULL	CTI Channel Out Status Register
CM0P_CTI_CTLGATE	0xF0002140	FULL	Enable CTI Channel Gate Register
CM0P_CTI_ASICCTL	0xF0002144	FULL	External Multiplexor Control Register
CM0P_CTI_ITCHINACK	0xF0002EDC	FULL	ITCHINACK Register
CM0P_CTI_ITTRIGINACK	0xF0002EE0	FULL	ITTRIGINACK Register
CM0P_CTI_ITCHOUT	0xF0002EE4	FULL	ITCHOUT Register

Register Name	Address	Permission	Description
CM0P_CTI_ITTRIGOUT	0xF0002EE8	FULL	ITTRIGOUT Register
CM0P_CTI_ITCHOUTACK	0xF0002EEC	FULL	ITCHOUTACK Register
CM0P_CTI_ITTRIGOUTACK	0xF0002EF0	FULL	ITTRIGOUTACK Register
CM0P_CTI_ITCHIN	0xF0002EF4	FULL	ITCHIN Register
CM0P_CTI_ITTRIGIN	0xF0002EF8	FULL	ITTRIGIN Register
CM0P_CTI_ITCTRL	0xF0002F00	FULL	Integration Mode Control Register
CM0P_CTI_CLAIMSET	0xF0002FA0	FULL	Claim Tag Set Register
CM0P_CTI_CLAIMCLR	0xF0002FA4	FULL	Claim Tag Clear Register
CM0P_CTI_LOCKACCESS	0xF0002FB0	FULL	Lock Access Register
CM0P_CTI_LOCKSTATUS	0xF0002FB4	FULL	Lock Status Register
CM0P_CTI_AUTHSTATUS	0xF0002FB8	FULL	Authentication Status Register
CM0P_CTI_DEVID	0xF0002FC8	FULL	Device Configuration Register
CM0P_CTI_DEVTYPE	0xF0002FCC	FULL	Device Type Identifier Register
CM0P_CTI_PID4	0xF0002FD0	FULL	Peripheral Identification Register 4
CM0P_CTI_PID5	0xF0002FD4	FULL	Peripheral Identification Register 5
CM0P_CTI_PID6	0xF0002FD8	FULL	Peripheral Identification Register 6
CM0P_CTI_PID7	0xF0002FDC	FULL	Peripheral Identification Register 7
CM0P_CTI_PID0	0xF0002FE0	FULL	Peripheral Identification Register 0
CM0P_CTI_PID1	0xF0002FE4	FULL	Peripheral Identification Register 1
CM0P_CTI_PID2	0xF0002FE8	FULL	Peripheral Identification Register 2
CM0P_CTI_PID3	0xF0002FEC	FULL	Peripheral Identification Register 3
CM0P_CTI_CID0	0xF0002FF0	FULL	Component Identification Register 0
CM0P_CTI_CID1	0xF0002FF4	FULL	Component Identification Register 1
CM0P_CTI_CID2	0xF0002FF8	FULL	Component Identification Register 2
CM0P_CTI_CID3	0xF0002FFC	FULL	Component Identification Register 3

3.7 MTB

Register Name	Address	Permission	Description
CM0P_MTB_POSITION	0xF0003000	FULL	POSITION register
CM0P_MTB_MASTER	0xF0003004	FULL	MASTER register
CM0P_MTB_FLOW	0xF0003008	FULL	FLOW register
CM0P_MTB_BASE	0xF000300C	FULL	BASE register
CM0P_MTB_LA	0xF0003FB0	FULL	Lock Access register
CM0P_MTB_LS	0xF0003FB4	FULL	Lock Status register
CM0P_MTB_AS	0xF0003FB8	FULL	Authentication Status register
CM0P_MTB_DARCH	0xF0003FBC	FULL	Device Architecture register
CM0P_MTB_DCFG	0xF0003FC8	FULL	Device Configuration register
CM0P_MTB_DID	0xF0003FCC	FULL	Device Type Identifier register.
CM0P_MTB_PID4	0xF0003FD0	FULL	Peripheral Identification Register 4.
CM0P_MTB_PID5	0xF0003FD4	FULL	Peripheral Identification Register 5.
CM0P_MTB_PID6	0xF0003FD8	FULL	Peripheral Identification Register 6.
CM0P_MTB_PID7	0xF0003FDC	FULL	Peripheral Identification Register 7.
CM0P_MTB_PID0	0xF0003FE0	FULL	Peripheral Identification Register 0.
CM0P_MTB_PID1	0xF0003FE4	FULL	Peripheral Identification Register 1.
CM0P_MTB_PID2	0xF0003FE8	FULL	Peripheral Identification Register 2.
CM0P_MTB_PID3	0xF0003FEC	FULL	Peripheral Identification Register 3.
CM0P_MTB_CID0	0xF0003FF0	FULL	Component Identification Register 0.
CM0P_MTB_CID1	0xF0003FF4	FULL	Component Identification Register 1.
CM0P_MTB_CID2	0xF0003FF8	FULL	Component Identification Register 2.
CM0P_MTB_CID3	0xF0003FFC	FULL	Component Identification Register 3.

3.8 Register Details

3.8.1 DWT

3.8.1.1 CM0P_DWT_DWT_CTRL

Description: Watchpoint Comparator Configuration
Address: 0xE0001000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Defines the number of comparators implemented
Default: 0x20000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	NUMCOMP [31:28]				None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
28:31	NUMCOMP	R	R	2	Number of comparators available

3.8.1.2 CM0P_DWT_DWT_PCSR

Description: Watchpoint Comparator PC Sample
Address: 0xE000101C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment: Samples the current value of the program counter. Unless DWT_PCSR reads as 0xFFFFFFFF, under the conditions described in Program counter sampling support on page C1-344, bit [0] is RAZ. When RAZ, bit [0] does not reflect instruction set state as is the case with similar functionality in other ARM architecture profiles.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EIASAMPLE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	EIASAMPLE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	EIASAMPLE [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	EIASAMPLE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	EIASAMPLE	R	R	X	Executed Instruction Address sample value

3.8.1.3 CM0P_DWT_DWT_COMP0

Description: Watchpoint Comparator Compare Value
Address: 0xE0001020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: Provides a reference value for use by comparator
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	X	Reference value for comparison. See The DWT comparators on page C1-341.

3.8.1.4 CM0P_DWT_DWT_MASK0

Description: Watchpoint Comparator Mask
Address: 0xE0001024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: Provides the size of the ignore mask applied to the access address range matching
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MASK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MASK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	MASK	RW	RW	X	The size of the ignore mask applied to address range matching. See The DWT comparators on page C1-341 for the usage model. The mask range is IMPLEMENTATION DEFINED. Writing all ones to this field and reading it back can be used to determine the maximum mask size supported.

3.8.1.5 CM0P_DWT_DWT_FUNCTION0

Description: Watchpoint Comparator Function
Address: 0xE0001028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment: Controls the operation of the comparator
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				FUNCTION [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Select action on comparator match.
	DISABLE			0	Disabled
	IADDR			4	PC watchpoint event
	DADDR_RO			5	Watchpoint event
	DADDR_WO			6	Watchpoint event
	DADDR_RW			7	Watchpoint event
24	MATCHED	R	R	0	Comparator match. It indicates that the operation defined by FUNCTION has occurred since the bit was last read: 0 the associated comparator has matched. 1 the associated comparator has not matched. Reading the register clears this bit to 0.

3.8.1.6 CM0P_DWT_DWT_COMP1

Description: Watchpoint Comparator Compare Value
Address: 0xE0001030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment: Provides a reference value for use by comparator
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	X	Reference value for comparison. See The DWT comparators on page C1-341.

3.8.1.7 CM0P_DWT_DWT_MASK1

Description: Watchpoint Comparator Mask
Address: 0xE0001034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment: Provides the size of the ignore mask applied to the access address range matching
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MASK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MASK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	MASK	RW	RW	X	The size of the ignore mask applied to address range matching. See The DWT comparators on page C1-341 for the usage model. The mask range is IMPLEMENTATION DEFINED. Writing all ones to this field and reading it back can be used to determine the maximum mask size supported.

3.8.1.8 CM0P_DWT_DWT_FUNCTION1

Description: Watchpoint Comparator Function
Address: 0xE0001038
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment: Controls the operation of the comparator
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				FUNCTION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Select action on comparator match.
	DISABLE			0	Disabled
	IADDR			4	PC watchpoint event
	DADDR_RO			5	Watchpoint event
	DADDR_WO			6	Watchpoint event
	DADDR_RW			7	Watchpoint event
24	MATCHED	R	R	0	Comparator match. It indicates that the operation defined by FUNCTION has occurred since the bit was last read: 0 the associated comparator has matched. 1 the associated comparator has not matched. Reading the register clears this bit to 0.

3.8.1.9 CM0P_DWT_DWT_PID4

Description: Watchpoint Unit CoreSight ROM Table Peripheral ID #4
Address: 0xE0001FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

3.8.1.10 CM0P_DWT_DWT_PID0

Description: Watchpoint Unit CoreSight ROM Table Peripheral ID #0
Address: 0xE0001FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xA

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	10	Peripheral ID #0

3.8.1.11 CM0P_DWT_DWT_PID1

Description: Watchpoint Unit CoreSight ROM Table Peripheral ID #1
Address: 0xE0001FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	Peripheral ID #1

3.8.1.12 CM0P_DWT_DWT_PID2

Description: Watchpoint Unit CoreSight ROM Table Peripheral ID #2
Address: 0xE0001FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

3.8.1.13 CM0P_DWT_DWT_PID3

Description: Watchpoint Unit CoreSight ROM Table Peripheral ID #3
Address: 0xE0001FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

3.8.1.14 CM0P_DWT_DWT_CID0

Description: Watchpoint Unit CoreSight ROM Table Component ID #0
Address: 0xE0001FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

3.8.1.15 CM0P_DWT_DWT_CID1

Description: Watchpoint Unit CoreSight ROM Table Component ID #1
Address: 0xE0001FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	Component ID #1

3.8.1.16 CM0P_DWT_DWT_CID2

Description: Watchpoint Unit CoreSight ROM Table Component ID #2
Address: 0xE0001FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

3.8.1.17 CM0P_DWT_DWT_CID3

Description: Watchpoint Unit CoreSight ROM Table Component ID #3
Address: 0xE0001FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

3.8.2 BP

3.8.2.1 CM0P_BP_BP_CTRL

Description: Breakpoint Unit Control
Address: 0xE0002000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Provides BPU implementation information, and the global enable for the BPU.
Default: 0x40

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NUM_CODE [7:4]				None [3:2]		KEY [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the BPU: 0 BPU is disabled. 1 BPU is enabled.
1	KEY	RW	RW	0	RAZ on reads, SBO for writes. If written as zero, the write to the register is ignored.
4:7	NUM_CODE	R	R	4	The number of breakpoint comparators. If NUM_CODE is zero, the implementation does not support any comparators.

3.8.2.2 CM0P_BP_BP_COMP0

Description: Breakpoint Compare Register
Address: 0xE0002008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: Holds a breakpoint address for comparison with instruction addresses in the Code memory region, see The system address map on page B3-258 for more information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	COMP_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MATCH [31:30]		None [29:29]	COMP_ADDR [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the comparator: Note BP_CTRL.ENABLE must also be set to 1 to enable a comparator.
2:28	COMP_ADDR	RW	RW	X	Stores bits [28:2] of the comparison address. The comparison address is compared with the address from the Code memory region. Bits [31:29] and [1:0] of the comparison address are zero.
30:31	MATCH	RW	RW	X	BP_MATCH defines the behavior when the COMP address is matched.
	NONE			0	No breakpoint matching
	LOWER			1	Breakpoint on lower halfword, upper is unaffected.
	UPPER			2	Breakpoint on upper halfword, lower is unaffected.
	BOTH			3	Breakpoint on both lower and upper halfwords.

3.8.2.3 CM0P_BP_BP_COMP1

Description: Breakpoint Compare Register
Address: 0xE000200C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Holds a breakpoint address for comparison with instruction addresses in the Code memory region, see The system address map on page B3-258 for more information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	COMP_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MATCH [31:30]		None [29:29]	COMP_ADDR [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the comparator: Note BP_CTRL.ENABLE must also be set to 1 to enable a comparator.
2:28	COMP_ADDR	RW	RW	X	Stores bits [28:2] of the comparison address. The comparison address is compared with the address from the Code memory region. Bits [31:29] and [1:0] of the comparison address are zero.
30:31	MATCH	RW	RW	X	BP_MATCH defines the behavior when the COMP address is matched.
	NONE			0	No breakpoint matching
	LOWER			1	Breakpoint on lower halfword, upper is unaffected.
	UPPER			2	Breakpoint on upper halfword, lower is unaffected.
	BOTH			3	Breakpoint on both lower and upper halfwords.

3.8.2.4 CM0P_BP_BP_COMP2

Description: Breakpoint Compare Register
Address: 0xE0002010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Holds a breakpoint address for comparison with instruction addresses in the Code memory region, see The system address map on page B3-258 for more information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	COMP_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MATCH [31:30]		None [29:29]	COMP_ADDR [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the comparator: Note BP_CTRL.ENABLE must also be set to 1 to enable a comparator.
2:28	COMP_ADDR	RW	RW	X	Stores bits [28:2] of the comparison address. The comparison address is compared with the address from the Code memory region. Bits [31:29] and [1:0] of the comparison address are zero.
30:31	MATCH	RW	RW	X	BP_MATCH defines the behavior when the COMP address is matched.
	NONE			0	No breakpoint matching
	LOWER			1	Breakpoint on lower halfword, upper is unaffected.
	UPPER			2	Breakpoint on upper halfword, lower is unaffected.
	BOTH			3	Breakpoint on both lower and upper halfwords.

3.8.2.5 CM0P_BP_BP_COMP3

Description: Breakpoint Compare Register
Address: 0xE0002014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: Holds a breakpoint address for comparison with instruction addresses in the Code memory region, see The system address map on page B3-258 for more information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	COMP_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MATCH [31:30]		None [29:29]	COMP_ADDR [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the comparator. Note BP_CTRL.ENABLE must also be set to 1 to enable a comparator.
2:28	COMP_ADDR	RW	RW	X	Stores bits [28:2] of the comparison address. The comparison address is compared with the address from the Code memory region. Bits [31:29] and [1:0] of the comparison address are zero.
30:31	MATCH	RW	RW	X	BP_MATCH defines the behavior when the COMP address is matched.
	NONE			0	No breakpoint matching
	LOWER			1	Breakpoint on lower halfword, upper is unaffected.
	UPPER			2	Breakpoint on upper halfword, lower is unaffected.
	BOTH			3	Breakpoint on both lower and upper halfwords.

3.8.2.6 CM0P_BP_BP_PID4

Description: Breakpoint Unit CoreSight ROM Table Peripheral ID #4
Address: 0xE0002FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

3.8.2.7 CM0P_BP_BP_PID0

Description: Breakpoint Unit CoreSight ROM Table Peripheral ID #0
Address: 0xE0002FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #0

3.8.2.8 CM0P_BP_BP_PID1

Description: Breakpoint Unit CoreSight ROM Table Peripheral ID #1
Address: 0xE0002FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	Peripheral ID #1

3.8.2.9 CM0P_BP_BP_PID2

Description: Breakpoint Unit CoreSight ROM Table Peripheral ID #2
Address: 0xE0002FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

3.8.2.10 CM0P_BP_BP_PID3

Description: Breakpoint Unit CoreSight ROM Table Peripheral ID #3
Address: 0xE0002FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

3.8.2.11 CM0P_BP_BP_CID0

Description: Breakpoint Unit CoreSight ROM Table Component ID #0
Address: 0xE0002FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

3.8.2.12 CM0P_BP_BP_CID1

Description: Breakpoint Unit CoreSight ROM Table Component ID #1
Address: 0xE0002FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	Component ID #1

3.8.2.13 CM0P_BP_BP_CID2

Description: Breakpoint Unit CoreSight ROM Table Component ID #2
Address: 0xE0002FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

3.8.2.14 CM0P_BP_BP_CID3

Description: Breakpoint Unit CoreSight ROM Table Component ID #3
Address: 0xE0002FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

3.8.3 SCS

3.8.3.1 CM0P_SCS_SYST_CSR

Description: SysTick Control & Status
Address: 0xE000E010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Controls the SysTick counter and provides status data. The SysTick counter is functional in the Active and Sleep power modes (and not functional in the DeepSleep, and Hibernate power modes).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CLKSOURCE [2:2]	TICKINT [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							COUNTFLAG [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Indicates the enabled status of the SysTick counter: '0': counter is disabled. '1': counter is operating.
1	TICKINT	RW	RW	0	Indicates whether counting to '0' causes the status of the SysTick exception to change to pending: '0': count to '0' does not affect the SysTick exception status. '1': count to '0' changes the SysTick exception status to pending. Changing the value of the counter to '0' by writing zero to the SYST_CVR register to '0' never changes the status of the SysTick exception.
2	CLKSOURCE	RW	RW	0	Indicates the SysTick counter clock source: '0': SysTick uses the low frequency clock 'clk_lf'. For this mode to function, 'clk_lf' should be less than half the frequency of 'clk_sys'. Note that 'clk_lf' is generated by a low accuracy ILO (Internal Low power Oscillator), with a target frequency of 32.768 kHz (frequency can be as low as 15 KHz and as high as 60 kHz). '1': SysTick uses the system/processor clock 'clk_sys'. In PSoC4A-BLE (and later products), SysTick counter functionality on the low frequency clock is provided. In SF, TSG6M products, this functionality is not provided. For these products, this field should be set to '1', such that SysTick uses the system clock 'clk_sys'.

Bits	Name	SW	HW	Default or Enum	Description
16	COUNTFLAG	R	R	0	Indicates whether the counter has counted to '0' since the last read of this register: '0': counter has not counted to '0'. '1': counter has counted to '0'. COUNTFLAG is set to '1' by a count transition from '1' to '0'. COUNTFLAG is cleared to '0' by a read of this register, and by any write to the SYST_CVR register.

3.8.3.2 CM0P_SCS_SYST_RVR

Description: SysTick Reload Value
Address: 0xE000E014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: Sets or reads the reload value of the SYST_CVR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RELOAD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RELOAD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RELOAD [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	RELOAD	RW	RW	X	The value to load into the SYST_CVR register when the counter reaches 0.

3.8.3.3 CM0P_SCS_SYST_CVR

Description: SysTick Current Value
Address: 0xE000E018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: Reads or clears the current counter value. Any write to the register clears the register to 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CURRENT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CURRENT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CURRENT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	CURRENT	RW	RW	X	Current counter value. This is the value of the counter at the time it is sampled.

3.8.3.4 CM0P_SCS_SYST_CALIB

Description: SysTick Calibration Value
Address: 0xE000E01C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment: Reads the calibration value and parameters for SysTick.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TENMS [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TENMS [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TENMS [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	NOREF [31:31]	SKEW [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	TENMS	R	R	X	Optionally, holds a reload value to be used for 10ms (100Hz) timing, subject to system clock skew errors. If this field is '0', the calibration value is not known. In PSoC4A-BLE (and later products), SysTick counter functionality on the low frequency clock is provided and this field is 0x00:00147. In earlier products, SysTick counter functionality on the low frequency clock is NOT provided and this field is 0x00:0000.
30	SKEW	R	R	X	Indicates whether the 10ms calibration value is exact: '0': 10ms calibration value is exact. '1': 10ms calibration value is inexact, because of the clock frequency. In PSoC4A-BLE (and later products), SysTick counter functionality on the low frequency clock is provided and this field is '1' (due to the low accuracy ILO). In earlier products, SysTick counter functionality on the low frequency clock is NOT provided and this field is '0'.
31	NOREF	R	R	0	Indicates whether a implementation defined reference clock is provided: '0': the reference clock is provided. '1': the reference clock is not provided. When this bit is '1', the SYST_CSR.CLKSOURCE is forced to '1' and cannot be cleared to '0'. In PSoC4A-BLE (and later products), SysTick counter functionality on the low frequency clock is provided and this field is '0'. In earlier products, SysTick counter functionality on the low frequency clock is NOT provided and this field is '1'.

3.8.3.5 CM0P_SCS_ISR

Description: Interrupt Set-Enable Register
Address: 0xE000E100
Offset: 0x100
Retention: Retained
IsDeepSleep: No
Comment: Enables, or reads the enabled state of one or more interrupts.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SETENA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SETENA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SETENA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SETENA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SETENA	RW1S	RW1S	0	Enables, or reads the enabled state of one or more interrupts. Each bit corresponds to the same numbered interrupt.

3.8.3.6 CM0P_SCS_ICER

Description: Interrupt Clear Enable Register
Address: 0xE000E180
Offset: 0x180
Retention: Retained
IsDeepSleep: No
Comment: Disables, or reads the enabled state of one or more interrupts
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CLRENA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CLRENA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CLRENA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CLRENA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CLRENA	RW1C	RW1C	0	Disables, or reads the enabled state of one or more interrupts. Each bit corresponds to the same numbered interrupt.

3.8.3.7 CM0P_SCS_ISPR

Description: Interrupt Set-Pending Register
Address: 0xE000E200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment: On writes, sets the status of one or more interrupts to pending. On reads, shows the pending status of the interrupts.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SETPEND [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	SETPEND [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	SETPEND [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	SETPEND [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SETPEND	RW1S	RW1S	0	Changes the state of one or more interrupts to pending. Each bit corresponds to the same numbered interrupt.

3.8.3.8 CM0P_SCS_ICPR

Description: Interrupt Clear-Pending Register
Address: 0xE000E280
Offset: 0x280
Retention: Retained
IsDeepSleep: No
Comment: On writes, clears the status of one or more interrupts to pending. On reads, shows the pending status of the interrupts.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CLRPEND [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CLRPEND [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	CLRPEND [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CLRPEND [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CLRPEND	RW1C	RW1C	0	Changes the state of one or more interrupts to not pending. Each bit corresponds to the same numbered interrupt.

3.8.3.9 CM0P_SCS_IPR

Description: Interrupt Priority Registers
Address: 0xE000E400
Offset: 0x400
Retention: Retained
IsDeepSleep: No
Comment: Sets or reads interrupt priorities. Register n contains priorities for interrupts $N=4n \dots 4n+3$
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PRI_N0 [7:6]		None [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	PRI_N1 [15:14]		None [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	PRI_N2 [23:22]		None [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	PRI_N3 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
6:7	PRI_N0	RW	RW	0	Priority of interrupt number N.
14:15	PRI_N1	RW	RW	0	Priority of interrupt number N+1.
22:23	PRI_N2	RW	RW	0	Priority of interrupt number N+2.
30:31	PRI_N3	RW	RW	0	Priority of interrupt number N+3.

3.8.3.10 CM0P_SCS_CPUID

Description: CPUID Register
Address: 0xE000ED00
Offset: 0xD00
Retention: Retained
IsDeepSleep: No
Comment: Contains the part number, version, and implementation information that is specific to this processor.
Default: 0x410CC601

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REVISION [3:0]							
Bits	15	14	13	12	11	10	9	8
Name	PARTNO [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	VARIANT [23:20]				CONSTANT [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	IMPLEMENTER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	REVISION	R	R	1	Indicates revision. In ARM implementations this is the minor revision number n in the pn part of the rnpn revision status, see Product revision status on page xii. For release r0p1.
4:15	PARTNO	R	R	3168	Indicates part number, Cortex-M0+
16:19	CONSTANT	R	R	12	Indicates the architecture, ARMv6-M
20:23	VARIANT	R	R	0	Implementation defined. In ARM implementations this is the major revision number n in the rn part of the rnpn revision status, Product revision status on page xii.
24:31	IMPLEMENTER	R	R	65	Implementer code for ARM.

3.8.3.11 CM0P_SCS_ICSR

Description: Interrupt Control State Register
Address: 0xE000ED04
Offset: 0xD04
Retention: Retained
IsDeepSleep: No
Comment: Controls and provides status information for the ARMv6-M.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VECTACTIVE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name					None [11:9]			VECTACTIV E [8:8]

Bits	23	22	21	20	19	18	17	16
Name	ISRPREEMP T [23:23]	ISRPENDIN G [22:22]	None [21:21]	VECTPENDING [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	NMIPENDSE T [31:31]	None [30:29]		PENDSVSET [28:28]	PENDSVCLR [27:27]	PENDSTSET B [26:26]	PENDSTCLR [25:25]	None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	VECTACTIVE	R	R	0	The exception number for the current executing exception. 0= Thread mode. This is the same value as IPSR[8:0]
12:20	VECTPENDING	R	R	0	The exception number for the highest priority pending exception. 0= No pending exceptions. The pending state includes the effect of memory-mapped enable and mask registers. It does not include the PRIMASK special-purpose register qualifier.
22	ISRPENDING	R	R	0	Indicates if an external configurable, NVIC generated, interrupt is pending.
23	ISRPREEMPT	R	R	0	Indicates whether a pending exception will be serviced on exit from debug halt state.
25	PENDSTCLR	RW1C	RW1C	0	Clears a pending SysTick, whether set here or by the timer hardware.
26	PENDSTSETB	RW1S	RW1S	0	Sets a pending SysTick or reads back the current state. Writing PENDSTSET and PENDSTCLR to '1' concurrently is UNPREDICTABLE.
27	PENDSVCLR	RW1C	RW1C	0	Clears a pending PendSV interrupt.
28	PENDSVSET	RW1S	RW1S	0	Sets a pending PendSV interrupt or reads back the current state. Use this normally to request a context switch. Writing PENDSVSET and PENDSVCLR to '1' concurrently is UNPREDICTABLE.
31	NMIPENDSET	RW1S	RW1S	0	Activates an NMI exception or reads back the current state. Because NMI is the highest priority exception, it activates as soon as it is registered.

3.8.3.12 CM0P_SCS_VTOR

Description: Vector Table Offset Register
Address: 0xE000ED08
Offset: 0xD08
Retention: Retained
IsDeepSleep: No
Comment: Holds the vector table offset address
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TBLOFF [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TBLOFF [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TBLOFF [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:31	TBLOFF	RW	RW	0	Table offset address. All bits of the Vector table address that are not defined by the VTOR are zero.

3.8.3.13 CM0P_SCS_AIRCR

Description: Application Interrupt and Reset Control Register
Address: 0xE000ED0C
Offset: 0xD0C
Retention: Retained
IsDeepSleep: No
Comment: Sets or returns interrupt control data.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					SYSRESETREQ [2:2]	VECTCLRACTIVE [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	ENDIANNESS [15:15]	None [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	VECTKEY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	VECTCLRACTIVE	RW1C	RW1C	0	Clears all active state information for fixed and configurable exceptions. The effect of writing a 1 to this bit if the processor is not halted in Debug state is UNPREDICTABLE.
2	SYSRESETREQ	RW1S	RW1S	0	System Reset Request. Writing 1 to this bit asserts a signal to request a reset by the external system. This will cause a full system reset of the CPU and all other components in the device. See Reset management on page B1-240 for more information.
15	ENDIANNESS	R	R	0	Indicates the memory system data endianness: 0 little endian 1 big endian. See Endian support on page A3-44 for more information.
16:31	VECTKEY	RW	RW	X	Vector Key. The value 0x05FA must be written to this register, otherwise the register write is not performed.

3.8.3.14 CM0P_SCS_SCR

Description: System Control Register
Address: 0xE000ED10
Offset: 0xD10
Retention: Retained
IsDeepSleep: No
Comment: Sets or returns system control data.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SEVONPEND [4:4]	None [3:3]	SLEEPDEEP [2:2]	SLEEPONEX IT [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	SLEEPONEXIT	RW	RW	0	Determines whether, on an exit from an ISR that returns to the base level of execution priority, the processor enters a sleep state: 0 do not enter sleep state. 1 enter sleep state. See Power management on page B1-240 for more information.
2	SLEEPDEEP	RW	RW	0	An implementation can use this bit to select DeepSleep power modes upon execution of WFI/WFE: 0: Select Sleep mode 1: Select DeepSleep
4	SEVONPEND	RW	RW	0	Determines whether an interrupt transition from inactive state to pending state is a wakeup event: 0: transitions from inactive to pending are not wakeup events. 1: transitions from inactive to pending are wakeup events. See WFE on page A6-197 for more information.

3.8.3.15 CM0P_SCS_CCR

Description: Configuration and Control Register
Address: 0xE000ED14
Offset: 0xD14
Retention: Retained
IsDeepSleep: No
Comment: Returns configuration and control data.
Default: 0x208

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				UNALIGN_TRP [3:3]	None [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						STKALIGN [9:9]	None [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3	UNALIGN_TRP	R	R	1	1: unaligned word and halfword accesses generate a HardFault exception.
9	STKALIGN	R	R	1	1: On exception entry, the SP used prior to the exception is adjusted to be 8-byte aligned and the context to restore it is saved. The SP is restored on the associated exception return.

3.8.3.16 CM0P_SCS_SHPR2

Description: System Handler Priority Register 2
Address: 0xE000ED1C
Offset: 0xD1C
Retention: Retained
IsDeepSleep: No
Comment: Sets or returns priority for system handler 11
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PRI_11 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30:31	PRI_11	RW	RW	0	Priority of system handler 11, SVCall

3.8.3.17 CM0P_SCS_SHPR3

Description: System Handler Priority Register 3
Address: 0xE000ED20
Offset: 0xD20
Retention: Retained
IsDeepSleep: No
Comment: Sets or returns priority for system handlers 14-15.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PRI_14 [23:22]		None [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	PRI_15 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
22:23	PRI_14	RW	RW	0	Priority of system handler 14, PendSV
30:31	PRI_15	RW	RW	0	Priority of system handler 15, SysTick

3.8.3.18 CM0P_SCS_SHCSR

Description: System Handler Control and State Register
Address: 0xE000ED24
Offset: 0xD24
Retention: Retained
IsDeepSleep: No
Comment: Controls and provides the status of system handlers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SVCALLPEN DED [15:15]	None [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
15	SVCALLPENDED	RW	RW	0	0 SVCall is not pending. 1 SVCall is pending. This bit reflects the pending state on a read, and updates the pending state, to the value written, on a write. (Pending state bits are set to 1 when an exception occurs, and are cleared to 0 when an exception becomes active.)

3.8.3.19 CM0P_SCS_DFSR

Description: Debug Fault Status Register
Address: 0xE000ED30
Offset: 0xD30
Retention: Retained
IsDeepSleep: No
Comment: Provides the top level reason why a debug event has occurred. Writing 1 to a register bit clears that bit to 0. A read of the HALTED bit by an instruction executed by stepping returns an UNKNOWN value, For more information see Debug stepping on page C1-325.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			EXTERNAL [4:4]	VCATCH [3:3]	DWTTRAP [2:2]	BKPT [1:1]	HALTED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	HALTED	RW1C	RW1C	0	Indicates a debug event generated by a C_HALT or C_STEP request, triggered by a write to the DHCSR: 0 no active halt request debug event. 1 halt request debug event active. See Debug Halting Control and Status Register, DHCSR for more information.
1	BKPT	RW1C	RW1C	0	Indicates a debug event generated by BKPT instruction execution or a breakpoint match in the BPU: 0 no breakpoint debug event. 1 at least one breakpoint debug event.
2	DWTTRAP	RW1C	RW1C	0	Indicates a debug event generated by the DWT: 0 no debug events generated by the DWT. 1 at least one debug event generated by the DWT.
3	VCATCH	RW1C	RW1C	0	Indicates whether a vector catch debug event was generated: 0 no vector catch debug event generated. 1 vector catch debug event generated. The corresponding FSR shows the primary cause of the exception.
4	EXTERNAL	RW1C	RW1C	0	Indicates an asynchronous debug event generated because of EDBGRRQ being asserted: 0 no EDBGRRQ debug event. 1 EDBGRRQ debug event.

3.8.3.20 CM0P_SCS_MPU_TYPE

Description: MPU Type Register

Address: 0xE000ED90

Offset: 0xD90

Retention: Retained

IsDeepSleep: No

Comment: The MPU Type Register indicates how many regions the MPU supports. Software can use it to determine if the processor implements an MPU

Default: 0x800

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							SEPARATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DREGION [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	IREGION [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SEPARATE	R	R	0	Indicates support for separate instruction and data address maps. RAZ. ARMv6-M only supports a unified MPU.
8:15	DREGION	R	R	8	Number of regions supported by the MPU. If this field reads-as-zero the processor does not implement an MPU.
16:23	IREGION	R	R	0	Instruction region. RAZ. ARMv6-M only supports a unified MPU.

3.8.3.21 CM0P_SCS_MPU_CTRL

Description: MPU Control Register

Address: 0xE000ED94

Offset: 0xD94

Retention: Retained

IsDeepSleep: No

Comment: Enables the MPU, and when the MPU is enabled, controls whether the default memory map is enabled as a background region for privileged accesses, and whether the MPU is enabled for HardFaults and NMI.

If no regions are enabled and the PRIVDEFENA and ENABLE bits are set, only privileged code can execute from the system address map.

If the MPU is not implemented, this register is RAZ/WI.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					PRIVDEFEN A [2:2]	HFNMIEA [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enables the MPU: 0: The MPU is disabled. Privileged and unprivileged accesses use the default memory map. 1: The MPU is enabled.
1	HFNMIEA	RW	RW	0	The meaning of this bit is: 0: disables the MPU for HardFaults and NMIs. 1: when the ENABLE bit is set to 1, enables the MPU for HardFaults and NMIs. Note: If HFNMIEA is set to 1 when ENABLE is set to 0, behavior is UNPREDICTABLE.
2	PRIVDEFENA	RW	RW	0	When the ENABLE bit is set to 1, the meaning of this bit is: 0: Disables the default memory map. Any instruction or data access that does not access a defined region faults. 1: Enables the default memory map as a background region for privileged access. The system address map on page B3-258 describes the default memory map. When the ENABLE bit is set to 0, the processor ignores the PRIVDEFENA bit.

3.8.3.22 CM0P_SCS_MPU_RNR

Description: MPU Region Number Register

Address: 0xE000ED98

Offset: 0xD98

Retention: Retained

IsDeepSleep: No

Comment: Selects the region currently accessed by MPU_RBAR and MPU_RASR.
Used with MPU_RBAR and MPU_RASR, see MPU Region Base Address Register, MPU_RBAR, and MPU Region Attribute and Size Register, MPU_RASR.
If an implementation supports N regions then the regions number from 0 to (N-1), and the effect of writing a value of N or greater to the REGION field is UNPREDICTABLE.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REGION_M [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	REGION_M	RW	RW	X	Indicates the memory region accessed by MPU_RBAR and MPU_RSAR. Normally, software must write the required region number to MPU_RNR to select the required memory region, before accessing MPU_RBAR or MPU_RSAR. However, the MPU_RBAR.VALID bit provides an alternative way of writing to MPU_RBAR to update a region base address without first writing the region number to MPU_RNR, see MPU Region Base Address Register, MPU_RBAR.

3.8.3.23 CM0P_SCS_MPU_RBAR

Description:	MPU Region Base Address Register
Address:	0xE000ED9C
Offset:	0xD9C
Retention:	Retained
IsDeepSleep:	No
Comment:	Holds the base address of the region identified by MPU_RNR. On a write, can also be used to update the base address of a specified region, in the range 0 to 15, updating MPU_RNR with the new region number. Normally, used with MPU_RBAR, see MPU Region Number Register, MPU_RNR. If an implementation supports N regions then the regions number from 0 to (N-1). If N is less than 16 the effect of writing a value of N or greater to the REGION field is UNPREDICTABLE. Software can find the minimum size of region supported by an MPU region by writing all ones to MPURBAR[31:5] for that region, and then reading the register to find the value saved to bits [31:5]. The number of trailing zeros in this bit field indicates the minimum supported alignment and therefore the supported region size. An implementation must support all region size values from the minimum supported to 4GB, see the description of the MPU_RASR.SIZE field in MPU Region Attribute and Size Register, MPU_RASR. Software must ensure that the value written to the ADDR field aligns with the size of the selected region.
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			VALID [4:4]	REGION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	REGION	RW	RW	X	On writes, can specify the number of the region to update, see VALID field description. On reads, returns bits [3:0] of MPU_RNR.
4	VALID	RW	RW	X	On writes to the register, indicates whether the write must update the base address of the region identified by the REGION field. updating the MPU_RNR to indicate this new region: 0 Update the base address of the region indicated by MPU_RNR, ignoring the value of the REGION field. 1 Update the least-significant four bits of the MPU_RNR.REGION field with MPU_RBAR.REGION field value, writing 0b0000 to bits [7:4] of the MPU_RBAR.REGION field, and updating the base address of that region. This bit reads as zero
8:31	ADDR	RW	RW	X	Base address of the region.

3.8.3.24 CM0P_SCS_MPU_RASR

Description: MPU Region Attribute and Size Register

Address: 0xE000EDA0

Offset: 0xDA0

Retention: Retained

IsDeepSleep: No

Comment: Defines the size, access behavior, and memory type of the region identified by MPU_RNR, and enables that region.

Used with MPU_RBAR, see MPU Region Number Register, MPU_RNR on. Writing a SIZE value greater than the maximum size supported by the corresponding MPU_RBAR has an UNPREDICTABLE effect. The smallest supported region size is 256 bytes. This restricts the lowest possible value of SIZE.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		SIZE [5:1]					ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	SRD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ATTRS [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ATTRS [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	X	Enables this region: 0: when the MPU is enabled, this region is disabled. 1: When the MPU is enabled, this region is enabled. Enabling a region has no effect unless the MPU_CTRL.ENABLE bit is set to 1, to enable the MPU.
1:5	SIZE	RW	RW	X	Indicates the region size. The permitted values for SIZE are 7-31, that is 0b00111-0b11111. The associated region size, in bytes, is $2^{(SIZE+1)}$. SIZE field values less than 7 are reserved, because the smallest supported region size is 256 bytes.
8:15	SRD	RW	RW	X	Subregion Disable. For regions of 256 bytes or larger, each bit of this field controls whether one of the eight equal subregions is enabled. 0: subregion enabled. 1: subregion disabled.
16:31	ATTRS	RW	RW	X	The MPU Region Attribute field, This field has the following subfields, defined in Region attribute control on page B3-300 of the ARMv6M Architecture manual (September 2010 version): XN MPU_RASR[28] AP[2:0] MPU_RASR[26:24] TEX[2:0] MPU_RASR[21:19] S MPU_RASR[18] C MPU_RASR[17] B MPU_RASR[16]

3.8.3.25 CM0P_SCS_DHCSR

Description: Debug Halting Control and Status Register
Address: 0xE000EDF0
Offset: 0xDF0
Retention: Retained
IsDeepSleep: No
Comment: Controls halting debug. When C_DEBUGEN is set to 1, C_STEP and C_MASKINTS must not be modified when the processor is running. Note: S_HALT is 0 when the processor is running. When C_DEBUGEN is set to 0, the processor ignores the values of all other bits in this register. For more information on the use of DHCSR, see Debug stepping on page C1-325. Note: any write to this register must have [31:16]=0xA05F - if not, the write is ignored.
Default: 0x2000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				C_MASKINTS [3:3]	C_STEP [2:2]	C_HALT [1:1]	C_DEBUGEN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DBG_KEY_P1 [23:20]				S_LOCKUP [19:19]	S_SLEEP [18:18]	S_HALT [17:17]	S_REGRDY [16:16]

Bits	31	30	29	28	27	26	25	24
Name	DBG_KEY_P2 [31:26]						S_RESET_ST [25:25]	S_RETIRE_ST [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	C_DEBUGEN	RW	RW	0	Halting debug enable bit. If a debugger writes to DHCSR to change the value of this bit from 0 to 1, it must also write 0 to the C_MASKINTS bit, otherwise behavior is UNPREDICTABLE. This bit can only be written from the DAP. Access to the DHCSR from software running on the processor is IMPLEMENTATION DEFINED. However, writes to this bit from software running on the processor are ignored.
1	C_HALT	RW	RW	X	Processor halt bit. The effects of writes to this bit are: 0 Request a halted processor to run. 1 Request a running processor to halt. Table C1-7 on page C1-326 shows the effect of writes to this bit when the processor is in Debug state.
2	C_STEP	RW	RW	X	Processor step bit. The effects of writes to this bit are: 0 Single-stepping disabled. 1 Single-stepping enabled. For more information about the use of this bit see Table C1-7 on page C1-326.

Bits	Name	SW	HW	Default or Enum	Description
3	C_MASKINTS	RW	RW	X	When debug is enabled, the debugger can write to this bit to mask PendSV, SysTick and external configurable interrupts. The effect of any attempt to change the value of this bit is UNPREDICTABLE unless both: - before the write to DHCSR, the value of the C_HALT bit is 1 - the write to the DHCSR that changes the C_MASKINTS bit also writes 1 to the C_HALT bit This means that a single write to DHCSR cannot set the C_HALT to 0 and change the value of the C_MASKINTS bit. The bit does not affect NMI. When DHCSR.C_DEBUGEN is set to 0, the value of this bit is UNKNOWN. For more information about the use of this bit see Table C1-7 on page C1-326.
16	S_REGRDY	R	R	X	A handshake flag for transfers through the DCRDR: - Writing to DCRSR clears the bit to 0. - Completion of the DCRDR transfer then sets the bit to 1. For more information about DCRDR transfers see Debug Core Register Data Register, DCRDR on page C1-337. 0: There has been a write to the DCRDR, but the transfer is not complete. 1: The transfer to or from the DCRDR is complete. This bit is only valid when the processor is in Debug state, otherwise the bit is UNKNOWN.
17	S_HALT	R	R	0	Indicates whether the processor is in Debug state.
18	S_SLEEP	R	R	0	Indicates whether the processor is sleeping. The debugger must set the DHCSR.C_HALT bit to 1 to gain control, or wait for an interrupt or other wakeup event to wakeup the system.
19	S_LOCKUP	R	R	0	Indicates whether the processor is locked up because of an unrecoverable exception. See Unrecoverable exception cases on page B1-238 for more information. This bit can only read as 1 when accessed by a remote debugger using the DAP. The bit clears to 0 when the processor enters Debug state.
20:23	DBG_KEY_P1	W	W	X	Debug key: Software must write 0xA05F to [31:16] to enable write accesses to bits [15:0], otherwise the processor ignores the write access.
24	S_RETIRE_ST	R	R	X	When not in Debug state, indicates whether the processor has completed execution of at least one instruction since the last read of DHCSR. This is a sticky bit, that clears to 0 on a read of DHCSR. This bit is UNKNOWN: - after a Local reset, but is set to 1 as soon as the processor completes execution of an instruction - when S_LOCKUP is set to 1 - when S_HALT is set to 1. When the processor is not in Debug state, a debugger can check this bit to determine if the processor is stalled on a load, store or fetch access.
25	S_RESET_ST	R	R	1	Indicates whether the processor has been reset since the last read of DHCSR. This is a sticky bit, that clears to 0 on a read of DHCSR
26:31	DBG_KEY_P2	W	W	X	See description for Bit 20

3.8.3.26 CM0P_SCS_DCRSR

Description: Debug Core Register Selector Register

Address: 0xE00EDF4

Offset: 0xDF4

Retention: Retained

IsDeepSleep: No

Comment: With the DCRDR, see Debug Core Register Data Register, DCRDR on page C1-337, the DCRSR provides debug access to the ARM core registers and special-purpose registers. A write to DCRSR specifies the register to transfer, whether the transfer is a read or a write, and starts the transfer. This register is only accessible in Debug state. When the processor is in Debug state, the debugger must preserve the Exception number bits in the IPSR, otherwise behavior is UNPREDICTABLE

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			REGSEL [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							REGWNR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	REGSEL	RW	RW	X	Specifies the ARM core register or special-purpose register to transfer.
	R0			0	CPU R0
	R1			1	CPU R1
	R2			2	CPU R2
	R3			3	CPU R3
	R4			4	CPU R4
	R5			5	CPU R5
	R6			6	CPU R6
	R7			7	CPU R7
	R8			8	CPU R8
	R9			9	CPU R9
	R10			10	CPU R10
	R11			11	CPU R11
	R12			12	CPU R12
	SP			13	Current Stack Pointer
	LR			14	CPU LR
	DBG_RA			15	DebugReturnAddress: the address of the first instruction to be executed on exit from Debug state.
	XPSR			16	xPSR
	MSP			17	Main stack pointer, MSP.
	PSP			18	Process stack pointer, PSP
	C_P			20	[31:24]: CONTROL [7:0]: PRIMASK.
16	REGWNR	RW	RW	X	Specifies the type of access for the transfer.
	READ			0	Read transfer

Bits	Name	SW	HW	Default or Enum	Description
	WRITE			1	Write transfer

3.8.3.27 CM0P_SCS_DCRDR

Description: Debug Core Register Data Register
Address: 0xE000EDF8
Offset: 0xDF8
Retention: Retained
IsDeepSleep: No
Comment: With the DCRSR, see Debug Core Register Selector Register, DCRSR on page C1-335, the DCRDR provides debug access to the ARM core registers and special-purpose registers. The DCRDR is the data register for these accesses.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DBGTMP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DBGTMP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DBGTMP [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DBGTMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DBGTMP	RW	RW	X	Data temporary cache, for reading and writing CPU registers. This register is UNKNOWN: - on reset - when DHCSR.S_HALT = 0. - when DHCSR.S_REGRDY = 0 during execution of a DCRSR based transaction that updates the register

3.8.3.28 CM0P_SCS_DEMCR

Description: Debug Exception and Monitor Control Register
Address: 0xE000EDFC
Offset: 0xDFC
Retention: Retained
IsDeepSleep: No
Comment: Manages vector catch behavior and enables the DWT.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							VC_CORERESET [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					VC_HARDERR [10:10]	None [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							DWTENA [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	VC_CORERESET	RW	RW	0	Enable Reset Vector Catch. This causes a Local reset to halt a running system. If DHCSR.C_DEBUGEN is set to 0, the processor ignores the value of this bit.
10	VC_HARDERR	RW	RW	0	Enable halting debug trap on a HardFault exception. If DHCSR.C_DEBUGEN is set to 0, the processor ignores the value of this bit.
24	DWTENA	RW	RW	0	Global enable for all features configured and controlled by the DWT unit. When DWTENA is set to 0 DWT registers return UNKNOWN values on reads. In addition, it is IMPLEMENTATION DEFINED whether the processor ignores writes to the DWT while DWTENA is 0.

3.8.3.29 CM0P_SCS_SCS_PID4

Description: System Control Space ROM Table Peripheral ID #4
Address: 0xE000EFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

3.8.3.30 CM0P_SCS_SCS_PID0

Description: System Control Space ROM Table Peripheral ID #0
Address: 0xE000EFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x8

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	8	Peripheral ID #0

3.8.3.31 CM0P_SCS_SCS_PID1

Description: System Control Space ROM Table Peripheral ID #1
Address: 0xE000EFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	Peripheral ID #1

3.8.3.32 CM0P_SCS_SCS_PID2

Description: System Control Space ROM Table Peripheral ID #2
Address: 0xE000EFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

3.8.3.33 CM0P_SCS_SCS_PID3

Description: System Control Space ROM Table Peripheral ID #3
Address: 0xE000EFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

3.8.3.34 CM0P_SCS_SCS_CID0

Description: System Control Space ROM Table Component ID #0
Address: 0xE000EFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

3.8.3.35 CM0P_SCS_SCS_CID1

Description: System Control Space ROM Table Component ID #1
Address: 0xE000EFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	Component ID #1

3.8.3.36 CM0P_SCS_SCS_CID2

Description: System Control Space ROM Table Component ID #2
Address: 0xE000EFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

3.8.3.37 CM0P_SCS_SCS_CID3

Description: System Control Space ROM Table Component ID #3
Address: 0xE000E0FC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

3.8.4 ROM

3.8.4.1 CM0P_ROM_ROM_SCS

Description: CM0+ CoreSight ROM Table Peripheral #0
Address: 0xE00FF000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF0F003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429398016 3	Offset to SCS ROM Table

3.8.4.2 CM0P_ROM_ROM_DWT

Description: CM0+ CoreSight ROM Table Peripheral #1
Address: 0xE00FF004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF02003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4293926915	Offset to DWT ROM Table

3.8.4.3 CM0P_ROM_ROM_BPU

Description: CM0+ CoreSight ROM Table Peripheral #2
Address: 0xE00FF008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF03003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429393101 1	Offset to BPU ROM Table

3.8.4.4 CM0P_ROM_ROM_END

Description: CM0+ CoreSight ROM Table End Marker
Address: 0xE00FF00C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	End marker in peripheral list

3.8.4.5 CM0P_ROM_ROM_CSMT

Description: CM0+ CoreSight ROM Table Memory Type
Address: 0xE00FFFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Memory Type

3.8.4.6 CM0P_ROM_ROM_PID4

Description: CM0+ CoreSight ROM Table Peripheral ID #4
Address: 0xE00FFFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

3.8.4.7 CM0P_ROM_ROM_PID0

Description: CM0+ CoreSight ROM Table Peripheral ID #0
Address: 0xE00FFFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	192	Peripheral ID #0

3.8.4.8 CM0P_ROM_ROM_PID1

Description: CM0+ CoreSight ROM Table Peripheral ID #1
Address: 0xE00FFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	180	Peripheral ID #1

3.8.4.9 CM0P_ROM_ROM_PID2

Description: CM0+ CoreSight ROM Table Peripheral ID #2
Address: 0xE00FFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

3.8.4.10 CM0P_ROM_ROM_PID3

Description: CM0+ CoreSight ROM Table Peripheral ID #3
Address: 0xE00FFFE0
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

3.8.4.11 CM0P_ROM_ROM_CID0

Description: CM0+ CoreSight ROM Table Component ID #0
Address: 0xE00FFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

3.8.4.12 CM0P_ROM_ROM_CID1

Description: CM0+ CoreSight ROM Table Component ID #1
Address: 0xE00FFFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component ID #1

3.8.4.13 CM0P_ROM_ROM_CID2

Description: CM0+ CoreSight ROM Table Component ID #2
Address: 0xE00FFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

3.8.4.14 CM0P_ROM_ROM_CID3

Description: CM0+ CoreSight ROM Table Component ID #3
Address: 0xE00FFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

3.8.5 ROMTABLE

3.8.5.1 CM0P_ROMTABLE_ADDR0

Description: Link to Cortex M0+ ROM Table.
Address: 0xF0000000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xF00FF003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						FORMAT_32BIT [1:1]	PRESENT [0:0]

Bits	15	14	13	12	11	10	9	8
Name						None [11:8]		

Bits	23	22	21	20	19	18	17	16
Name	ADDR_OFFSET [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR_OFFSET [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PRESENT	R	R	1	Entry present.
1	FORMAT_32BIT	R	R	1	ROM Table format: '0': 8-bit format. '1': 32-bit format.
12:31	ADDR_OFFSET	R	R	983295	Address offset of the Cortex-M0 ROM Table base address (0xe00f:f000) wrt. Cypress chip specific ROM Table base address (0xf000:0000). ADDR_OFFSET[19:0] = 0xe00f:f - 0xf000:0 = 0xf00f:f.

3.8.5.2 CM0P_ROMTABLE_ADDR1

Description: Link to CoreSight CTI Table.
Address: 0xF0000004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						FORMAT_32BIT [1:1]	PRESENT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [11:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR_OFFSET [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR_OFFSET [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PRESENT	R	R	1	Entry present.
1	FORMAT_32BIT	R	R	1	ROM Table format: '0': 8-bit format. '1': 32-bit format.
12:31	ADDR_OFFSET	R	R	2	Address offset of the Cortex-M0 ROM Table base address (0xe00f:f000) wrt. Cypress chip specific ROM Table base address (0xf000:0000). ADDR_OFFSET[19:0] = 0xe00f:f - 0xf000:0 = 0xf00f:f.

3.8.5.3 CM0P_ROMTABLE_ADDR2

Description: Link to Cortex M0+ MTB Table.
Address: 0xF0000008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						FORMAT_32BIT [1:1]	PRESENT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [11:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR_OFFSET [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR_OFFSET [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PRESENT	R	R	1	Entry present.
1	FORMAT_32BIT	R	R	1	ROM Table format: '0': 8-bit format. '1': 32-bit format.
12:31	ADDR_OFFSET	R	R	3	Address offset of the Cortex-M0 ROM Table base address (0xe00f:f000) wrt. Cypress chip specific ROM Table base address (0xf000:0000). ADDR_OFFSET[19:0] = 0xe00f:f - 0xf000:0 = 0xf00f:f.

3.8.5.4 CM0P_ROMTABLE_DID

Description: Device Type Identifier register.
Address: 0xF0000FCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	.

3.8.5.5 CM0P_ROMTABLE_PID4

Description: Peripheral Identification Register 4.
Address: 0xF0000FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT [7:4]				JEP_CONTINUATION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	JEP_CONTINUATION	R	R	Undefined	JEP106 continuation code. This value is product specific and specified as part of the product definition in the CPUSS.JEPCONTINUATION parameter.
4:7	COUNT	R	R	0	Size of ROM Table is $2^{\text{COUNT}} * 4$ KByte.

3.8.5.6 CM0P_ROMTABLE_PID5

Description: Peripheral Identification Register 5.
Address: 0xF0000FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

3.8.5.7 CM0P_ROMTABLE_PID6

Description: Peripheral Identification Register 6.
Address: 0xF0000FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

3.8.5.8 CM0P_ROMTABLE_PID7

Description: Peripheral Identification Register 7.
Address: 0xF0000FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

3.8.5.9 CM0P_ROMTABLE_PID0

Description: Peripheral Identification Register 0.
Address: 0xF0000FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PN_MIN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	PN_MIN	R	R	Undefined	JEP106 part number. 4 lsb of CPUSS.PARTNUMBER parameter. These part numbers are maintained in spec 40-9500.

3.8.5.10 CM0P_ROMTABLE_PID1

Description: Peripheral Identification Register 1.
Address: 0xF0000FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	JEPID_MIN [7:4]				PN_MAJ [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PN_MAJ	R	R	Undefined	JEP106 part number. 4 msbs of CPUSS.PARTNUMBER parameter. These part numbers are maintained in spec 40-9500.
4:7	JEPID_MIN	R	R	Undefined	JEP106 vendor id. 4 lsbs of CPUSS.JEPID parameter. This number is maintained in spec 40-9500.

3.8.5.11 CM0P_ROMTABLE_PID2

Description: Peripheral Identification Register 2.
Address: 0xF0000FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REV [7:4]				None [3:3]	JEPID_MAJ [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	JEPID_MAJ	R	R	Undefined	JEP106 vendor id. 4 msbs of CPUSS.JEPID parameter. This number is maintained in spec 40-9500.
4:7	REV	R	R	Undefined	Major REVersion number (chip specific). Identifies the design iteration of the component. For first tape out: 0x1. This field is implemented in RTL by an ECO-able tie-off structure and is incremented on subsequent tape outs.

3.8.5.12 CM0P_ROMTABLE_PID3

Description: Peripheral Identification Register 3.
Address: 0xF0000FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REV_AND [7:4]				CM [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CM	R	R	0	N/A
4:7	REV_AND	R	R	Undefined	Minor REVision number (chip specific). For first tape out: 0x1. This field is incremented on subsequent tape outs.

3.8.5.13 CM0P_ROMTABLE_CID0

Description: Component Identification Register 0.
Address: 0xF0000FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component identification byte 0 of 4-byte component identification 0xB105:100D.

3.8.5.14 CM0P_ROMTABLE_CID1

Description: Component Identification Register 1.
Address: 0xF0000FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component identification byte 1 of 4-byte component identification 0xB105:100D. Component class: 'ROM Table'.

3.8.5.15 CM0P_ROMTABLE_CID2

Description: Component Identification Register 2.
Address: 0xF0000FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component identification byte 2 of 4-byte component identification 0xB105:100D.

3.8.5.16 CM0P_ROMTABLE_CID3

Description: Component Identification Register 3.
Address: 0xF0000FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component identification byte 3 of 4-byte component identification 0xB105:100D.

3.8.6 CTI

3.8.6.1 CM0P_CTI_CTICONTROL

Description: CTI Control Register
Address: 0xF0002000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: The CTI Control Register enables the CTI.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							GLBEN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GLBEN	RW	RW	0	Enables or disables the ECT: 0 = disabled (reset) 1 = enabled. When disabled, all cross triggering mapping logic functionality is disabled for this processor.

3.8.6.2 CM0P_CTLI_INTACK

Description: CTI Interrupt Acknowledge Register

Address: 0xF0002010

Offset: 0x10

Retention: Retained

IsDeepSleep: No

Comment: The CTI Interrupt Acknowledge Register is write-only. Any bits written as a 1 cause the CTITRIGOUT output signal to be acknowledged. The acknowledgement is cleared when MAPTRIGOUT is deactivated. This register is used when the CTITRIGOUT is used as a sticky output, that is, no hardware acknowledge is supplied, and a software acknowledge is required.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INTACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INTACK	W	W	0	Acknowledges the corresponding CTITRIGOUT output: 1 = CTITRIGOUT is acknowledged and is cleared when MAPTRIGOUT is LOW. 0 = no effect. There is one bit of the register for each CTITRIGOUT output.

3.8.6.3 CM0P_CTLIAPPSET

Description: CTI Application Trigger Set Register
Address: 0xF0002014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Set Register is read/write. A write to this register causes a channel event to be raised, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPSET [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPSET	RW	RW	0	Setting a bit HIGH generates a channel event for the selected channel. Read: 0 = application trigger inactive (reset) 1 = application trigger active. Write: 0 = no effect 1 = generate channel event. There is one bit of the register for each channel.

3.8.6.4 CM0P_CTI_APPCLEAR

Description: CTI Application Trigger Clear Register
Address: 0xF0002018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Clear Register is write-only. A write to this register causes a channel event to be cleared, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPCLEAR [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPCLEAR	W	W	0	Clears corresponding bits in the CTIAPPSET register. 1 = application trigger disabled in the CTIAPPSET register 0 = no effect. There is one bit of the register for each channel.

3.8.6.5 CM0P_CTI_APPULSE

Description: CTI Application Pulse Register

Address: 0xF000201C

Offset: 0x1C

Retention: Retained

IsDeepSleep: No

Comment: The CTI Application Pulse Register is write-only. A write to this register causes a channel event pulse, one CTICLK period, to be generated, corresponding to the bit written to. The pulse external to the ECT can be extended to multi-cycle by the handshaking interface circuits. This register clears itself immediately, so it can be repeatedly written to without software having to clear it.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPULSE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPULSE	W	W	0	Setting a bit HIGH generates a channel event pulse for the selected channel. Write: 1 = channel event pulse generated for one CTICLK period 0 = no effect. There is one bit of the register for each channel.

3.8.6.6 CM0P_CTLI_CTIIEN

Description: CTI Trigger to Channel Enable Registers
Address: 0xF0002020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger to Channel Enable Registers enable the signalling of an event on CTM channels when the core issues a trigger, CTITRIGIN, to the CTI. There is one register for each of the eight CTITRIGIN inputs. Within each register there is one bit for each of the four channels implemented. These registers do not affect the application trigger operations.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGINEN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGINEN	RW	RW	0	Enables a cross trigger event to the corresponding channel when an CTITRIGIN is activated. 1 = enables the CTITRIGIN signal to generate an event on the respective channel of the CTM. There is one bit of the register for each of the four channels. For example in register CTIINEN0, TRIGINEN[0] set to 1 enables CTITRIGIN onto channel 0. 0 = disables the CTITRIGIN signal from generating an event on the respective channel of the CTM.

3.8.6.7 CM0P_CTLIOUTEN

Description: CTI Channel to Trigger Enable Registers

Address: 0xF00020A0

Offset: 0xA0

Retention: Retained

IsDeepSleep: No

Comment: The CTI Channel to Trigger Enable Registers define which channels can generate a CTITRIGOUT output. There is one register for each of the eight CTITRIGOUT outputs. Within each register there is one bit for each of the four channels implemented. These registers affect the mapping from application trigger to trigger outputs.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGOUTEN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGOUTEN	RW	RW	0	Changing the value of this bit from a 0 to a 1 enables a channel event for the corresponding channel to generate an CTITRIGOUT output: 0 = the channel input (CTICHIN) from the CTM is not routed to the CTITRIGOUT output 1 = the channel input (CTICHIN) from the CTM is routed to the CTITRIGOUT output. There is one bit for each of the four channels. For example in register CTIOUTEN0, enabling bit 0 enables CTICHIN[0] to cause a trigger event on the CTITRIGOUT[0] output.

3.8.6.8 CM0P_CTL_CTITRIGINSTATUS

Description: CTI Trigger In Status Register
Address: 0xF0002130
Offset: 0x130
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger In Status Register provides the status of the CTITRIGIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGINSTATUS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGINSTATUS	R	R	0	Shows the status of the CTITRIGIN inputs: 1 = CTITRIGIN is active 0 = CTITRIGIN is inactive. Because the register provides a view of the raw CTITRIGIN inputs, the reset value is unknown. There is one bit of the register for each trigger input.

3.8.6.9 CM0P_CTL_CTITRIGOUTSTATUS

Description: CTI Trigger Out Status Register
Address: 0xF0002134
Offset: 0x134
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger Out Status Register provides the status of the CTITRIGOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGOUTSTATUS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGOUTSTATUS	R	R	0	Shows the status of the CTITRIGOUT outputs. 1 = CTITRIGOUT is active 0 = CTITRIGOUT is inactive (reset). There is one bit of the register for each trigger output.

3.8.6.10 CM0P_CTICHINSTATUS

Description: CTI Channel In Status Register
Address: 0xF0002138
Offset: 0x138
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel In Status Register provides the status of the CTI CTICHIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHINSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHINSTATUS	R	R	0	Shows the status of the CTICHIN inputs: 1 = CTICHIN is active 0 = CTICHIN is inactive. Because the register provides a view of the raw CTICHIN inputs from the CTM, the reset value is unknown. There is one bit of the register for each channel input.

3.8.6.11 CM0P_CTICHIOUTSTATUS

Description: CTI Channel Out Status Register
Address: 0xF000213C
Offset: 0x13C
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel Out Status Register provides the status of the CTI CTICHOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHOUTSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHOUTSTATUS	R	R	0	Shows the status of the CTICHOUT outputs. 1 = CTICHOUT is active 0 = CTICHOUT is inactive (reset). There is one bit of the register for each channel output.

3.8.6.12 CM0P_CTI_CTIGATE

Description: Enable CTI Channel Gate Register

Address: 0xF0002140

Offset: 0x140

Retention: Retained

IsDeepSleep: No

Comment: The Gate Enable Register prevents the channels from propagating through the CTM to other CTIs. This enables local cross-triggering, for example for causing an interrupt when the ETM trigger occurs. It can be used effectively with CTIAPPSET, CTIAPPCLEAR, and CTIAPPPULSE for asserting trigger outputs by asserting channels, without affecting the rest of the system. On reset, this register is 0xF, and channel propagation is enabled.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTIGATEEN3 [3:3]	CTIGATEEN2 [2:2]	CTIGATEEN1 [1:1]	CTIGATEEN0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTIGATEEN0	RW	RW	1	Enable CTICHOUT0. Set to 0 to disable channel propagation.
1	CTIGATEEN1	RW	RW	1	Enable CTICHOUT1. Set to 0 to disable channel propagation.
2	CTIGATEEN2	RW	RW	1	Enable CTICHOUT2. Set to 0 to disable channel propagation.
3	CTIGATEEN3	RW	RW	1	Enable CTICHOUT3. Set to 0 to disable channel propagation.

3.8.6.13 CM0P_CTL_ASICCTL

Description: External Multiplexor Control Register
Address: 0xF0002144
Offset: 0x144
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ASICCTL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ASICCTL	RW	RW	0	Implementation-defined ASIC control, value written to the register is output on ASICCTL[7:0]. If external multiplexing of trigger signals is implemented then the number of multiplexed signals on each trigger must be reflected within the Device ID Register. This is done within a Verilog define EXTMUXNUM. See ECT CoreSight defined registers on page 4-28.

3.8.6.14 CM0P_CTLITCHINACK

Description: ITCHINACK Register
Address: 0xF0002EDC
Offset: 0xEDC
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHINACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHINACK	W	W	0	Set the value of the CTCHINACK outputs

3.8.6.15 CM0P_CTL_ITTRIGINACK

Description: ITTRIGINACK Register
Address: 0xF0002EE0
Offset: 0xEE0
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGINACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGINACK	W	W	0	Set the value of the CTTRIGINACK outputs

3.8.6.16 CM0P_CTLITCHOUT

Description: ITCHOUT Register
Address: 0xF0002EE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUT [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUT	W	W	0	Set the value of the CTCHOUT outputs

3.8.6.17 CM0P_CTL_ITTRIGOUT

Description: ITTRIGOUT Register
Address: 0xF0002EE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUT	W	W	0	Set the value of the CTTRIGOUT outputs

3.8.6.18 CM0P_CTL_ITCHOUTACK

Description: ITCHOUTACK Register
Address: 0xF0002EEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUTACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUTACK	R	R	0	Read the values of the CTCHOUTACK inputs

3.8.6.19 CM0P_CTL_ITTRIGOUTACK

Description: ITTRIGOUTACK Register
Address: 0xF0002EF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUTACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUTACK	R	R	0	Read the values of the CTTRIGOUTACK inputs

3.8.6.20 CM0P_CTLITCHIN

Description: ITCHIN Register
Address: 0xF0002EF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHIN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHIN	R	R	0	Read the values of the CTCHIN inputs

3.8.6.21 CM0P_CTL_ITTRIGIN

Description: ITTRIGIN Register
Address: 0xF0002EF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGIN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGIN	R	R	0	Read the values of the CTTRIGIN inputs

3.8.6.22 CM0P_CTI_ITCTRL

Description: Integration Mode Control Register

Address: 0xF0002F00

Offset: 0xF00

Retention: Retained

IsDeepSleep: No

Comment: This register enables the component to switch from a functional mode, the default behavior, to integration mode where the inputs and outputs of the component can be directly controlled for the purpose of integration testing and topology solving.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MODE	RW	RW	0	When set, the component enters integration mode, enabling topology detection or integration testing to be performed. At reset the component must enter functional mode. If no integration functionality is implemented, this register must read as zero.

3.8.6.23 CM0P_CTI_CLAIMSET

Description: Claim Tag Set Register

Address: 0xF0002FA0

Offset: 0xFA0

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location allows individual bits to be set, write, and returns the number of bits that can be set, read.
You can determine how many claim bits are implemented by reading this register. For example, if 4 bits are implemented, a read of this register will return 0x0000000F. If no claim tag is implemented, then a read of this register will return 0x00000000.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1S	RW1S	15	A bit programmable register bank which sets the Claim Tag Value. A read will return a logic 1 for all implemented locations.

3.8.6.24 CM0P_CTI_CLAIMCLR

Description: Claim Tag Clear Register

Address: 0xF0002FA4

Offset: 0xFA4

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location enables individual bits to be cleared, write, and returns the current Claim Tag value, read. The width (n) of this register can be determined from reading the Claim Tag Set Register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1C	RW1C	0	A bit programmable register bank that is zero at reset.

3.8.6.25 CM0P_CTI_LOCKACCESS

Description: Lock Access Register

Address: 0xF0002FB0

Offset: 0xFB0

Retention: Retained

IsDeepSleep: No

Comment: This is used to enable write access to device registers. If LOCKSTATUS[0] == 0x0 then this register is not present.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ACCESS_CODE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ACCESS_CODE	RW	RW	0	Write Access Code. A write of 0xC5ACCE55 enables further write access to this device. An invalid write will have the affect of removing write access. If LOCKSTATUS[2] is set, then only bits [7:0] of this register are implemented and lock access is obtained by consecutively writing 0xC5, 0xAC, 0xCE, 0x55. Bits [31:8] are unused and any writes to them ignored.

3.8.6.26 CM0P_CTI_LOCKSTATUS

Description: Lock Status Register

Address: 0xF0002FB4

Offset: 0xFB4

Retention: Retained

IsDeepSleep: No

Comment: This indicates the status of the Lock control mechanism. This lock prevents accidental writes by code under debug.

This register must always be present although there might not be any lock-access control mechanism. The lock mechanism, where present and locked, must block write accesses to any control register, except the Lock Access Register. For most components this covers all registers except for the Lock Access Register 0xFB0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					IMPLEMENT S_8B [2:2]	ACCESS _PE MITTED [1:1]	EXISTS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EXISTS	R	R	0	Indicates that a lock control mechanism exists for this device
1	ACCESS_PERMITTED	R	R	0	The values of this bit mean: 0 = Access permitted. 1 = Write access to the component is blocked. All writes to control registers are ignored. Reads are permitted
2	IMPLEMENTS_8B	R	R	0	This component implements an 8-bit Lock Access Register.

3.8.6.28 CM0P_CTL_DEVID

Description: Device Configuration Register

Address: 0xF0002FC8

Offset: 0xFC8

Retention: Retained

IsDeepSleep: No

Comment: This register is implementation-defined for each Part Number and Designer. This indicates the capabilities of the component. The entire 32-bit field can be used because the data width is determined by the particular component. Unused bits must read as zero.
If the component is configurable then it is recommended that this register reflects any changes to a standard configuration.

Default: 0x40804

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			NRMUXING [4:0]				
Bits	15	14	13	12	11	10	9	8
Name	NRTRIG [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				NRCHAN [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	NRMUXING	R	R	4	Indicates the number of multiplexing available on Trigger Inputs and Trigger Outputs using ASICCTL. Default value of 5'b00000 indicating no multiplexing present. Reflects the value of the Verilog `define EXTMUXNUM that you must alter accordingly.
8:15	NRTRIG	R	R	8	Number of ECT triggers available.
16:19	NRCHAN	R	R	4	Number of ECT channels available.

3.8.6.30 CM0P_CTL_PID4

Description: Peripheral Identification Register 4
Address: 0xF0002FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

3.8.6.31 CM0P_CTL_PID5

Description: Peripheral Identification Register 5
Address: 0xF0002FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.6.32 CM0P_CTL_PID6

Description: Peripheral Identification Register 6
Address: 0xF0002FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.6.33 CM0P_CTL_PID7

Description: Peripheral Identification Register 7
Address: 0xF0002FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.6.34 CM0P_CTL_PID0

Description: Peripheral Identification Register 0
Address: 0xF0002FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	6	N/A

3.8.6.35 CM0P_CTL_PID1

Description: Peripheral Identification Register 1
Address: 0xF0002FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	N/A

3.8.6.36 CM0P_CTI_PID2

Description: Peripheral Identification Register 2
Address: 0xF0002FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	43	N/A

3.8.6.37 CM0P_CTL_PID3

Description: Peripheral Identification Register 3
Address: 0xF0002FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision for MTB

3.8.6.38 CM0P_CTI_CID0

Description: Component Identification Register 0
Address: 0xF0002FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

3.8.6.39 CM0P_CTI_CID1

Description: Component Identification Register 1
Address: 0xF0002FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	N/A

3.8.6.40 CM0P_CTI_CID2

Description: Component Identification Register 2
Address: 0xF0002FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

3.8.6.41 CM0P_CTI_CID3

Description: Component Identification Register 3
Address: 0xF0002FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

3.8.7 MTB

3.8.7.1 CM0P_MTB_POSITION

Description: POSITION register

Address: 0xF0003000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: Contains the trace write pointer and the wrap bit. Available in all MTB configurations. You can modify all fields by software. Automatic hardware mechanisms update all fields. A debug agent might use the WRAP bit to determine whether the trace information above and below the pointer address is valid.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name						WRAP [2:2]	None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	POINTER [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	POINTER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	POINTER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2	WRAP	RW	RW	X	This bit is set to 1 automatically when the POINTER value wraps as determined by the MASTER.MASK field in the MASTER Trace Control Register.
3:31	POINTER	RW	RW	X	Trace packet location pointer. Because a packet consists of two words, the POINTER field is the location of the first word of a packet. This field contains bits [31:3] of the address, in the SRAM, where the next trace packet will be written. The field points to an unused location and is automatically incremented. A debug agent can calculate the system address, on the AHB-Lite bus, of the SRAM location pointed to by the POSITION register using the following equation: $\text{system address} = \text{BASE} + ((\text{P} + (2^{\text{AWIDTH}} - (\text{BASE} \bmod 2^{\text{AWIDTH}}))) \bmod 2^{\text{AWIDTH}}).$ Where P = POSITION AND 0xFFFF_FFF8. Where BASE is the BASE register value. Note: - The size of the SRAM is parameterized and the most significant bits of the POINTER field can be RAZ/WI, depending on the AWIDTH parameter value. - POSITION register bits greater than or equal to AWIDTH are RAZ/WI, therefore, the active POINTER field bits are [AWIDTH-4:0]. - The POINTER field value is relative to the base address of the SRAM in the system memory map.

3.8.7.2 CM0P_MTB_MASTER

Description: MASTER register

Address: 0xF0003004

Offset: 0x4

Retention: Retained

IsDeepSleep: No

Comment: Contains:

- The main trace enable bit.
- Other trace control fields.

Usage constraints - Before the MASTER.EN or MASTER.TSTARTEN bits are set to 1, software must initialize the POSITION and FLOW registers.

- If the FLOW.WATERMARK field is used to stop tracing or to halt the processor, the MASTER.MASK field must still be set to a value that prevents the POSITION.POINTER field from wrapping before it reaches the FLOW.WATERMARK value.
- The EDBGREQ output value is also affected by the Debug authentication interface.

Configurations: Available in all MTB configurations.

Attributes:

- You can modify all fields by software.
- Automatic hardware mechanisms update the EN and HALTREQ bits.

Following example MASK and POINTER values to illustrate the effect of the MASK field on the POINTER.

MASK POINTER POINTER + 1 POINTER next

0x0 0x1 0x2 0x0

0x0 0x5 0x6 0x4

0x3 0xF 0x10 0x0

0x3 0x1F 0x20 0x10

Default: 0x80

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SFRWPRIV [7:7]	TSTOPEN [6:6]	TSTARTEN [5:5]	MASK [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						HALTREQ [9:9]	RAMPRIV [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MASK	RW	RW	X	This value determines the maximum size of the trace buffer in SRAM. It specifies the most-significant bit of the POSITION.POINTER field that can be updated by automatic increment. If the trace tries to advance past this power of two, the POSITION.WRAP bit is set to 1, the POSITION.POINTER[MASK:0] bits are set to zero, and the POSITION.POINTER[AWIDTH-4:MASK+1] bits remain unchanged. This field causes the trace packet information to be stored in a circular buffer of size 2(MASK+4) bytes, that can be positioned in memory at multiples of this size. Valid values of this field are zero to AWIDTH-4. Values greater than the maximum have the same effect as the maximum.
5	TSTARTEN	RW	RW	0	Trace start input enable. If this bit is 1 and the TSTART signal is HIGH, then the EN bit is set to 1. Tracing continues until a stop condition occurs.
6	TSTOPEN	RW	RW	0	Trace stop input enable. If this bit is 1 and the TSTOP signal is HIGH, then the EN bit is set to 0. If a trace packet is being written to memory, the write is completed before tracing is stopped.
7	SFRWPRIV	RW	RW	1	Special Function Register Write Privilege bit. If this bit is 0, then User or Privileged AHB-Lite read and write accesses to the Special Function Registers are permitted. If this bit is 1, then only Privileged write accesses are permitted and User write accesses are ignored. The HPROT[1] signal determines if an access is User or Privileged. Note - SFR read accesses are not controlled by this bit and are always permitted. - This bit is implemented only if User/Privilege support is present in the MTB configuration. If User/Privilege support is absent, then the behavior of this bit is RAZ/WI and the value of the HPROT[1] signal is ignored.
8	RAMPRIV	RW	RW	0	SRAM Privilege bit. If this bit is 0, then User or Privileged AHB-Lite read and write accesses to the SRAM are permitted. If this bit is 1, then only Privileged AHB-Lite read and write accesses to the SRAM are permitted and User accesses are RAZ/WI. The HPROT[1] signal determines if an access is User or Privileged. Note This bit is implemented only if User/Privilege support is present in the MTB configuration. If User/Privilege support is absent, then the behavior of this bit is RAZ/WI and the value of the HPROT[1] signal is ignored.
9	HALTREQ	RW	RW	0	Halt request bit. This bit is connected to the halt request signal of the trace logic, EDBGRQ. When HALTREQ is set to 1, EDBGRQ is asserted if DBGEN is also HIGH. The HALTREQ bit can be automatically set to 1 using the FLOW.WATERMARK field.

Bits	Name	SW	HW	Default or Enum	Description
31	EN	RW	RW	0	Main trace enable bit. When this bit is 1 trace data is written into the SRAM memory location addressed by POSITION.POINTER. The POSITION.POINTER value auto increments after the trace data packet is written. The EN bit can be automatically set to 0 using the FLOW.WATERMARK field and the FLOW.AUTOSTOP bit. The EN bit is automatically set to 1 if the TSTARTEN bit is 1 and the TSTART signal is HIGH. The EN bit is automatically set to 0 if TSTOPEN bit is 1 and the TSTOP signal is HIGH. Note: If the EN bit is set to 0 because the FLOW.WATERMARK field is set, then it is not automatically set to 1 if the TSTARTEN bit is 1 and the TSTART input is HIGH. In this case tracing can only be restarted if the FLOW.WATERMARK or POSITION.POINTER value is changed by software.

3.8.7.3 CM0P_MTB_FLOW

Description: FLOW register

Address: 0xF0003008

Offset: 0x8

Retention: Retained

IsDeepSleep: No

Comment: Contains:

- The WATERMARK address.

- The AUTOSTOP and AUTOHALT control bits.

Usage constraints: There are no additional usage constraints.

Configurations: Available in all MTB configurations.

Attributes: You can modify all fields by software.

Note

- If you stop tracing, using the watermark auto stop feature, you cannot restart tracing until software clears the watermark auto stop. You can achieve this in one of the following ways:

- Changing the POSITION.POINTER field value to point to the beginning of the trace buffer.

- Setting the FLOW.AUTOSTOP bit to 0.

- A debug agent can use the AUTOSTOP bit to fill the trace buffer once only without halting the processor.

- A debug agent can use the AUTOHALT bit to fill the trace buffer once before causing the Cortex-M0+ processor to enter the Debug state. To enter Debug state, the Cortex-M0+ processor might have to perform additional branch type operations. Therefore you must set the WATERMARK field below the final entry in the trace buffer region.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name						None [2:2]	AUTOHALT [1:1]	AUTOSTOP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	WATERMARK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WATERMARK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WATERMARK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	AUTOSTOP	RW	RW	0	If this bit is 1 and WATERMARK is equal to POSITION.POINTER, then the MASTER.EN bit is automatically set to 0. This stops tracing.
1	AUTOHALT	RW	RW	0	If this bit is 1 and WATERMARK is equal to POSITION.POINTER, then the MASTER.HALTREQ bit is automatically set to 1. If the DBGGEN signal is HIGH, the MTB asserts this halt request to the Cortex-M0+ processor by asserting the EDBGREQ signal.
3:31	WATERMARK	RW	RW	X	WATERMARK value. This field contains an address in the same format as the POSITION.POINTER field. When the POSITION.POINTER matches the WATERMARK field value, actions defined by the AUTOHALT and AUTOSTOP bits are performed.

3.8.7.4 CM0P_MTB_BASE

Description: BASE register

Address: 0xF000300C

Offset: 0xC

Retention: Retained

IsDeepSleep: No

Comment: Purpose: Indicates where the SRAM is located in the processor memory map. This register is provided to enable auto discovery of the MTB SRAM location, by a debug agent.

Usage constraints: There are no additional usage constraints.

Configurations: Available in all MTB configurations.

Default: 0xF0010000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BASE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	BASE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BASE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BASE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	BASE	R	R	4026597376	The value provided is the value of the SRAMBASEADDR[31:0] signal. MTB SRAM base address in the processor memory map, which is fixed for this platform.

3.8.7.5 CM0P_MTB_LA

Description: Lock Access register
Address: 0xF0003FB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.6 CM0P_MTB_LS

Description: Lock Status register
Address: 0xF0003FB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.7 CM0P_MTB_AS

Description: Authentication Status register
Address: 0xF0003FB8
Offset: 0xFB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xA

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					AS_3 [3:3]	NIDEN [2:2]	AS_1 [1:1]	DBGEN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	AS_31TO4 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	AS_31TO4 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	AS_31TO4 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DBGEN	R	R	0	Invasive debug enable
1	AS_1	R	R	1	N/A
2	NIDEN	R	R	0	Non-invasive debug enable
3	AS_3	R	R	1	N/A
4:31	AS_31TO4	R	R	0	N/A

3.8.7.8 CM0P_MTB_DARCH

Description: Device Architecture register
Address: 0xF0003FBC
Offset: 0xFBC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x47700A31

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ARCH_ID [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ARCH_ID [15:8]							
Bits	23	22	21	20	19	18	17	16
Name				RES_20 [20:20]	REVISION [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	ARCHITECT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ARCH_ID	R	R	2609	Basic Trace Router Architecture Major Architecture Revision 0
16:19	REVISION	R	R	0	Minor Architecture Revision
20	RES_20	R	R	1	Reserved
21:31	ARCHITECT	R	R	571	Architect ARM

3.8.7.9 CM0P_MTB_DCFG

Description: Device Configuration register
Address: 0xF0003FC8
Offset: 0xFC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.10 CM0P_MTB_DID

Description: Device Type Identifier register.
Address: 0xF0003FCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x31

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUB_TYPE [7:4]				CLASS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CLASS	R	R	1	Trace Sink
4:7	SUB_TYPE	R	R	3	Basic Trace Router

3.8.7.11 CM0P_MTB_PID4

Description: Peripheral Identification Register 4.
Address: 0xF0003FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

3.8.7.12 CM0P_MTB_PID5

Description: Peripheral Identification Register 5.
Address: 0xF0003FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.13 CM0P_MTB_PID6

Description: Peripheral Identification Register 6.
Address: 0xF0003FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.14 CM0P_MTB_PID7

Description: Peripheral Identification Register 7.
Address: 0xF0003FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

3.8.7.15 CM0P_MTB_PID0

Description: Peripheral Identification Register 0.
Address: 0xF0003FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x32

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	50	N/A

3.8.7.16 CM0P_MTB_PID1

Description: Peripheral Identification Register 1.
Address: 0xF0003FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	N/A

3.8.7.17 CM0P_MTB_PID2

Description: Peripheral Identification Register 2.
Address: 0xF0003FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	27	N/A

3.8.7.18 CM0P_MTB_PID3

Description: Peripheral Identification Register 3.
Address: 0xF0003FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision for MTB

3.8.7.19 CM0P_MTB_CID0

Description: Component Identification Register 0.
Address: 0xF0003FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

3.8.7.20 CM0P_MTB_CID1

Description: Component Identification Register 1.
Address: 0xF0003FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	N/A

3.8.7.21 CM0P_MTB_CID2

Description: Component Identification Register 2.
Address: 0xF0003FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

3.8.7.22 CM0P_MTB_CID3

Description: Component Identification Register 3.
Address: 0xF0003FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4 CM7

Description	Cortex-M7 specific registers
Base Address	0xE0000000
Size	0x20000000
Slave Num	SYSTEM

4.1 ITM

Register Name	Address	Permission	Description
CM7_ITM_STIM0	0xE0000000	FULL	Stimulus Port registers
CM7_ITM_STIM1	0xE0000004	FULL	Stimulus Port registers
CM7_ITM_STIM2	0xE0000008	FULL	Stimulus Port registers
CM7_ITM_STIM3	0xE000000C	FULL	Stimulus Port registers
CM7_ITM_STIM4	0xE0000010	FULL	Stimulus Port registers
CM7_ITM_STIM5	0xE0000014	FULL	Stimulus Port registers
CM7_ITM_STIM6	0xE0000018	FULL	Stimulus Port registers
CM7_ITM_STIM7	0xE000001C	FULL	Stimulus Port registers
CM7_ITM_STIM8	0xE0000020	FULL	Stimulus Port registers
CM7_ITM_STIM9	0xE0000024	FULL	Stimulus Port registers
CM7_ITM_STIM10	0xE0000028	FULL	Stimulus Port registers
CM7_ITM_STIM11	0xE000002C	FULL	Stimulus Port registers
CM7_ITM_STIM12	0xE0000030	FULL	Stimulus Port registers
CM7_ITM_STIM13	0xE0000034	FULL	Stimulus Port registers
CM7_ITM_STIM14	0xE0000038	FULL	Stimulus Port registers
CM7_ITM_STIM15	0xE000003C	FULL	Stimulus Port registers
CM7_ITM_STIM16	0xE0000040	FULL	Stimulus Port registers
CM7_ITM_STIM17	0xE0000044	FULL	Stimulus Port registers
CM7_ITM_STIM18	0xE0000048	FULL	Stimulus Port registers
CM7_ITM_STIM19	0xE000004C	FULL	Stimulus Port registers
CM7_ITM_STIM20	0xE0000050	FULL	Stimulus Port registers
CM7_ITM_STIM21	0xE0000054	FULL	Stimulus Port registers
CM7_ITM_STIM22	0xE0000058	FULL	Stimulus Port registers
CM7_ITM_STIM23	0xE000005C	FULL	Stimulus Port registers
CM7_ITM_STIM24	0xE0000060	FULL	Stimulus Port registers
CM7_ITM_STIM25	0xE0000064	FULL	Stimulus Port registers
CM7_ITM_STIM26	0xE0000068	FULL	Stimulus Port registers
CM7_ITM_STIM27	0xE000006C	FULL	Stimulus Port registers
CM7_ITM_STIM28	0xE0000070	FULL	Stimulus Port registers
CM7_ITM_STIM29	0xE0000074	FULL	Stimulus Port registers
CM7_ITM_STIM30	0xE0000078	FULL	Stimulus Port registers
CM7_ITM_STIM31	0xE000007C	FULL	Stimulus Port registers
CM7_ITM_TER	0xE0000E00	FULL	Trace Enable Register
CM7_ITM_TPR	0xE0000E40	FULL	ITM Trace Privilege Register
CM7_ITM_TCR	0xE0000E80	FULL	Trace Control Register
CM7_ITM_ITATRDR	0xE0000EF0	FULL	Integration Mode Read ATB Ready
CM7_ITM_ITATVAL	0xE0000EF8	FULL	Integration Mode Write ATB Valid
CM7_ITM_TCTRL	0xE0000F00	FULL	Integration Mode Control Register
CM7_ITM_LAR	0xE0000FB0	FULL	Lock Access Register
CM7_ITM_LSR	0xE0000FB4	FULL	Lock Status Register
CM7_ITM_PID4	0xE0000FD0	FULL	Peripheral Identification Register 4.
CM7_ITM_PID5	0xE0000FD4	FULL	Peripheral Identification Register 5.
CM7_ITM_PID6	0xE0000FD8	FULL	Peripheral Identification Register 6.
CM7_ITM_PID7	0xE0000FDC	FULL	Peripheral Identification Register 7.
CM7_ITM_PID0	0xE0000FE0	FULL	Peripheral Identification Register 0.
CM7_ITM_PID1	0xE0000FE4	FULL	Peripheral Identification Register 1.
CM7_ITM_PID2	0xE0000FE8	FULL	Peripheral Identification Register 2.
CM7_ITM_PID3	0xE0000FEC	FULL	Peripheral Identification Register 3.
CM7_ITM_CID0	0xE0000FF0	FULL	Component Identification Register 0.
CM7_ITM_CID1	0xE0000FF4	FULL	Component Identification Register 1.
CM7_ITM_CID2	0xE0000FF8	FULL	Component Identification Register 2.
CM7_ITM_CID3	0xE0000FFC	FULL	Component Identification Register 3.

4.2 DWT

Register Name	Address	Permission	Description
CM7_DWT_CTRL	0xE0001000	FULL	Control register
CM7_DWT_CYCCNT	0xE0001004	FULL	Cycle Count register
CM7_DWT_CPICNT	0xE0001008	FULL	CPI Count register
CM7_DWT_EXCCNT	0xE000100C	FULL	Exception Overhead Count register
CM7_DWT_SLEPCNT	0xE0001010	FULL	Sleep Count register
CM7_DWT_LSUCNT	0xE0001014	FULL	LSU Count register
CM7_DWT_FOLDCNT	0xE0001018	FULL	Folded-instruction Count register
CM7_DWT_PCSR	0xE000101C	FULL	Program Counter Sample Register
CM7_DWT_COMP0	0xE0001020	FULL	Comparator registers
CM7_DWT_MASK0	0xE0001024	FULL	Comparator Mask registers
CM7_DWT_FUNCTION0	0xE0001028	FULL	Comparator Function registers
CM7_DWT_COMP1	0xE0001030	FULL	Comparator registers
CM7_DWT_MASK1	0xE0001034	FULL	Comparator Mask registers
CM7_DWT_FUNCTION1	0xE0001038	FULL	Comparator Function registers
CM7_DWT_COMP2	0xE0001040	FULL	Comparator registers
CM7_DWT_MASK2	0xE0001044	FULL	Comparator Mask registers
CM7_DWT_FUNCTION2	0xE0001048	FULL	Comparator Function registers
CM7_DWT_COMP3	0xE0001050	FULL	Comparator registers
CM7_DWT_MASK3	0xE0001054	FULL	Comparator Mask registers
CM7_DWT_FUNCTION3	0xE0001058	FULL	Comparator Function registers
CM7_DWT_LAR	0xE0001FB0	FULL	Lock Access Register
CM7_DWT_LSR	0xE0001FB4	FULL	Lock Status Register
CM7_DWT_PID4	0xE0001FD0	FULL	Peripheral Identification Register 4.
CM7_DWT_PID5	0xE0001FD4	FULL	Peripheral Identification Register 5.
CM7_DWT_PID6	0xE0001FD8	FULL	Peripheral Identification Register 6.
CM7_DWT_PID7	0xE0001FDC	FULL	Peripheral Identification Register 7.
CM7_DWT_PID0	0xE0001FE0	FULL	Peripheral Identification Register 0.
CM7_DWT_PID1	0xE0001FE4	FULL	Peripheral Identification Register 1.
CM7_DWT_PID2	0xE0001FE8	FULL	Peripheral Identification Register 2.
CM7_DWT_PID3	0xE0001FEC	FULL	Peripheral Identification Register 3.
CM7_DWT_CID0	0xE0001FF0	FULL	Component Identification Register 0.
CM7_DWT_CID1	0xE0001FF4	FULL	Component Identification Register 1.
CM7_DWT_CID2	0xE0001FF8	FULL	Component Identification Register 2.
CM7_DWT_CID3	0xE0001FFC	FULL	Component Identification Register 3.

4.3 FPB

Register Name	Address	Permission	Description
CM7_FPB_CTRL	0xE0002000	FULL	FlashPatch Control Register
CM7_FPB_REMAP	0xE0002004	FULL	FlashPatch Remap register
CM7_FPB_COMP0	0xE0002008	FULL	FlashPatch Comparator register
CM7_FPB_COMP1	0xE000200C	FULL	FlashPatch Comparator register
CM7_FPB_COMP2	0xE0002010	FULL	FlashPatch Comparator register
CM7_FPB_COMP3	0xE0002014	FULL	FlashPatch Comparator register
CM7_FPB_COMP4	0xE0002018	FULL	FlashPatch Comparator register
CM7_FPB_COMP5	0xE000201C	FULL	FlashPatch Comparator register
CM7_FPB_COMP6	0xE0002020	FULL	FlashPatch Comparator register
CM7_FPB_COMP7	0xE0002024	FULL	FlashPatch Comparator register
CM7_FPB_LAR	0xE0002FB0	FULL	Lock Access Register
CM7_FPB_LSR	0xE0002FB4	FULL	Lock Status Register
CM7_FPB_PID4	0xE0002FD0	FULL	Peripheral Identification Register 4.
CM7_FPB_PID5	0xE0002FD4	FULL	Peripheral Identification Register 5.
CM7_FPB_PID6	0xE0002FD8	FULL	Peripheral Identification Register 6.
CM7_FPB_PID7	0xE0002FDC	FULL	Peripheral Identification Register 7.
CM7_FPB_PID0	0xE0002FE0	FULL	Peripheral Identification Register 0.
CM7_FPB_PID1	0xE0002FE4	FULL	Peripheral Identification Register 1.
CM7_FPB_PID2	0xE0002FE8	FULL	Peripheral Identification Register 2.
CM7_FPB_PID3	0xE0002FEC	FULL	Peripheral Identification Register 3.
CM7_FPB_CID0	0xE0002FF0	FULL	Component Identification Register 0.
CM7_FPB_CID1	0xE0002FF4	FULL	Component Identification Register 1.
CM7_FPB_CID2	0xE0002FF8	FULL	Component Identification Register 2.

Register Name	Address	Permission	Description
CM7_FPB_CID3	0xE0002FFC	FULL	Component Identification Register 3.

4.4 SCS

Register Name	Address	Permission	Description
CM7_SCS_ACTLR	0xE000E008	FULL	Auxiliary Control Register
CM7_SCS_SYST_CSR	0xE000E010	FULL	SysTick Control and Status Register
CM7_SCS_SYST_RVR	0xE000E014	FULL	SysTick Reload Value Register
CM7_SCS_SYST_CVR	0xE000E018	FULL	SysTick Current Value Register
CM7_SCS_SYST_CALIB	0xE000E01C	FULL	SysTick Calibration value Register
CM7_SCS_NVIC_ISER0	0xE000E100	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER1	0xE000E104	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER2	0xE000E108	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER3	0xE000E10C	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER4	0xE000E110	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER5	0xE000E114	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER6	0xE000E118	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ISER7	0xE000E11C	FULL	Interrupt Set-Enable Registers
CM7_SCS_NVIC_ICER0	0xE000E180	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER1	0xE000E184	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER2	0xE000E188	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER3	0xE000E18C	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER4	0xE000E190	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER5	0xE000E194	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER6	0xE000E198	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ICER7	0xE000E19C	FULL	Interrupt Clear-Enable Registers
CM7_SCS_NVIC_ISPR0	0xE000E200	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR1	0xE000E204	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR2	0xE000E208	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR3	0xE000E20C	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR4	0xE000E210	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR5	0xE000E214	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR6	0xE000E218	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ISPR7	0xE000E21C	FULL	Interrupt Set-Pending Registers
CM7_SCS_NVIC_ICPR0	0xE000E280	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR1	0xE000E284	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR2	0xE000E288	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR3	0xE000E28C	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR4	0xE000E290	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR5	0xE000E294	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR6	0xE000E298	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_ICPR7	0xE000E29C	FULL	Interrupt Clear-Pending Registers
CM7_SCS_NVIC_IABR0	0xE000E300	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR1	0xE000E304	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR2	0xE000E308	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR3	0xE000E30C	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR4	0xE000E310	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR5	0xE000E314	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR6	0xE000E318	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IABR7	0xE000E31C	FULL	Interrupt Active Bit Registers
CM7_SCS_NVIC_IPR0	0xE000E400	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR1	0xE000E404	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR2	0xE000E408	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR3	0xE000E40C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR4	0xE000E410	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR5	0xE000E414	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR6	0xE000E418	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR7	0xE000E41C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR8	0xE000E420	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR9	0xE000E424	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR10	0xE000E428	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR11	0xE000E42C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR12	0xE000E430	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR13	0xE000E434	FULL	Interrupt Priority Registers

Register Name	Address	Permission	Description
CM7_SCS_NVIC_IPR14	0xE000E438	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR15	0xE000E43C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR16	0xE000E440	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR17	0xE000E444	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR18	0xE000E448	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR19	0xE000E44C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR20	0xE000E450	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR21	0xE000E454	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR22	0xE000E458	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR23	0xE000E45C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR24	0xE000E460	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR25	0xE000E464	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR26	0xE000E468	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR27	0xE000E46C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR28	0xE000E470	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR29	0xE000E474	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR30	0xE000E478	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR31	0xE000E47C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR32	0xE000E480	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR33	0xE000E484	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR34	0xE000E488	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR35	0xE000E48C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR36	0xE000E490	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR37	0xE000E494	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR38	0xE000E498	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR39	0xE000E49C	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR40	0xE000E4A0	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR41	0xE000E4A4	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR42	0xE000E4A8	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR43	0xE000E4AC	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR44	0xE000E4B0	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR45	0xE000E4B4	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR46	0xE000E4B8	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR47	0xE000E4BC	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR48	0xE000E4C0	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR49	0xE000E4C4	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR50	0xE000E4C8	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR51	0xE000E4CC	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR52	0xE000E4D0	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR53	0xE000E4D4	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR54	0xE000E4D8	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR55	0xE000E4DC	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR56	0xE000E4E0	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR57	0xE000E4E4	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR58	0xE000E4E8	FULL	Interrupt Priority Registers
CM7_SCS_NVIC_IPR59	0xE000E4EC	FULL	Interrupt Priority Registers
CM7_SCS_CPUID	0xE000ED00	FULL	CPUID Base Register
CM7_SCS_ICSR	0xE000ED04	FULL	Interrupt Control and State Register
CM7_SCS_VTOR	0xE000ED08	FULL	Vector Table Offset Register
CM7_SCS_AIRCR	0xE000ED0C	FULL	Application Interrupt and Reset Control Register
CM7_SCS_SCR	0xE000ED10	FULL	System Control Register
CM7_SCS_CCR	0xE000ED14	FULL	Configuration and Control Register
CM7_SCS_SHPR1	0xE000ED18	FULL	System Handler Priority Register 1
CM7_SCS_SHPR2	0xE000ED1C	FULL	System Handler Priority Register 2
CM7_SCS_SHPR3	0xE000ED20	FULL	System Handler Priority Register 3
CM7_SCS_SHCSR	0xE000ED24	FULL	System Handler Control and State Register
CM7_SCS_CFSR	0xE000ED28	FULL	Configurable Fault Status Register
CM7_SCS_HFSR	0xE000ED2C	FULL	HardFault Status Register
CM7_SCS_DFSR	0xE000ED30	FULL	Debug Fault Status Register
CM7_SCS_MMFAR	0xE000ED34	FULL	MemManage Fault Address Register
CM7_SCS_BFAR	0xE000ED38	FULL	BusFault Address Register
CM7_SCS_ID_PFR0	0xE000ED40	FULL	Processor Feature Register 0
CM7_SCS_ID_PFR1	0xE000ED44	FULL	Processor Feature Register 1

Register Name	Address	Permission	Description
CM7_SCS_ID_DFR0	0xE000ED48	FULL	Debug Feature Register 0
CM7_SCS_ID_AFR0	0xE000ED4C	FULL	Auxiliary Feature Register 0
CM7_SCS_ID_MMFR0	0xE000ED50	FULL	Memory Model Feature Register 0
CM7_SCS_ID_MMFR1	0xE000ED54	FULL	Memory Model Feature Register 1
CM7_SCS_ID_MMFR2	0xE000ED58	FULL	Memory Model Feature Register 2
CM7_SCS_ID_MMFR3	0xE000ED5C	FULL	Memory Model Feature Register 3
CM7_SCS_ID_ISAR0	0xE000ED60	FULL	Instruction Set Attributes Register 0
CM7_SCS_ID_ISAR1	0xE000ED64	FULL	Instruction Set Attributes Register 1
CM7_SCS_ID_ISAR2	0xE000ED68	FULL	Instruction Set Attributes Register 2
CM7_SCS_ID_ISAR3	0xE000ED6C	FULL	Instruction Set Attributes Register 3
CM7_SCS_ID_ISAR4	0xE000ED70	FULL	Instruction Set Attributes Register 4
CM7_SCS_CLIDR	0xE000ED78	FULL	Cache Level ID Register
CM7_SCS_CTR	0xE000ED7C	FULL	Cache Type Register
CM7_SCS_CCSIDR	0xE000ED80	FULL	Cache Size ID Register
CM7_SCS_CSSELR	0xE000ED84	FULL	Cache Size Selection Register
CM7_SCS_CPACR	0xE000ED88	FULL	Coprocessor Access Control Register
CM7_SCS_MPU_TYPE	0xE000ED90	FULL	MPU Type Register
CM7_SCS_MPU_CTRL	0xE000ED94	FULL	MPU Control Register
CM7_SCS_MPU_RNR	0xE000ED98	FULL	MPU Region Number Register
CM7_SCS_MPU_RBAR	0xE000ED9C	FULL	MPU Region Base Address Register
CM7_SCS_MPU_RASR	0xE000EDA0	FULL	MPU Region Attribute and Size Register
CM7_SCS_MPU_RBAR_A1	0xE000EDA4	FULL	MPU alias registers
CM7_SCS_MPU_RASR_A1	0xE000EDA8	FULL	MPU alias registers
CM7_SCS_MPU_RBAR_A2	0xE000EDAC	FULL	MPU alias registers
CM7_SCS_MPU_RASR_A2	0xE000EDB0	FULL	MPU alias registers
CM7_SCS_MPU_RBAR_A3	0xE000EDB4	FULL	MPU alias registers
CM7_SCS_MPU_RASR_A3	0xE000EDB8	FULL	MPU alias registers
CM7_SCS_DHCSR	0xE000EDF0	FULL	Debug Halting Control and Status Register
CM7_SCS_DCRSR	0xE000EDF4	FULL	Debug Core Register Selector Register
CM7_SCS_DCRDR	0xE000EDF8	FULL	Debug Core Register Data Register
CM7_SCS_DEMCR	0xE000EDFC	FULL	Debug Exception and Monitor Control Register
CM7_SCS_STIR	0xE000EF00	FULL	Software Triggered Interrupt Register
CM7_SCS_FPCCR	0xE000EF34	FULL	FP Context Control Register
CM7_SCS_FPCAR	0xE000EF38	FULL	FP Context Control Register
CM7_SCS_FPDSCR	0xE000EF3C	FULL	FP Context Control Register
CM7_SCS_MVFR0	0xE000EF40	FULL	Media and VFP Feature Register 0
CM7_SCS_MVFR1	0xE000EF44	FULL	Media and VFP Feature Register 1
CM7_SCS_MVFR2	0xE000EF48	FULL	Media and VFP Feature Register 2
CM7_SCS_ICIALLU	0xE000EF50	FULL	Instruction cache invalidate all to Point of Unification (PoU)
CM7_SCS_ICIMVAU	0xE000EF58	FULL	Instruction cache invalidate by address to PoU
CM7_SCS_DCIMVAC	0xE000EF5C	FULL	Data cache invalidate by address to Point of Coherency (PoC)
CM7_SCS_DCISW	0xE000EF60	FULL	Data cache invalidate by set/way
CM7_SCS_DCCMVAU	0xE000EF64	FULL	Data cache by address to PoU
CM7_SCS_DCCMVAC	0xE000EF68	FULL	Data cache clean by address to PoU
CM7_SCS_DCCSW	0xE000EF6C	FULL	Data cache clean by set/way
CM7_SCS_DCCIMVAC	0xE000EF70	FULL	Data cache clean and invalidate by address to PoC
CM7_SCS_DCCISW	0xE000EF74	FULL	Data cache clean and invalidate by set/way
CM7_SCS_CM7_ITCMCR	0xE000EF90	FULL	Instruction Tightly Coupled Memory Control Register
CM7_SCS_CM7_DTCMCR	0xE000EF94	FULL	Data Tightly Coupled Memory Control Register
CM7_SCS_CM7_AHBPCR	0xE000EF98	FULL	AHB Control Register
CM7_SCS_CM7_CACR	0xE000EF9C	FULL	L1 Cache Control Register
CM7_SCS_CM7_AHBSR	0xE000EFA0	FULL	AHB Slave Control Register
CM7_SCS_CM7_ABFSR	0xE000EFA8	FULL	Auxiliary Bus Fault Status Register
CM7_SCS_IEBR0	0xE000EFB0	FULL	Instruction Error bank Register 0
CM7_SCS_IEBR1	0xE000EFB4	FULL	Instruction Error bank Register 1
CM7_SCS_DEBR0	0xE000EFB8	FULL	Data Error Bank Register 0
CM7_SCS_DEBR1	0xE000EFBC	FULL	Data Error Bank Register 1
CM7_SCS_PID4	0xE000EFD0	FULL	Peripheral Identification Register 4
CM7_SCS_PID5	0xE000EFD4	FULL	Peripheral Identification Register 5
CM7_SCS_PID6	0xE000EFD8	FULL	Peripheral Identification Register 6

Register Name	Address	Permission	Description
CM7_SCS_PID7	0xE000EFD0	FULL	Peripheral Identification Register 7
CM7_SCS_PID0	0xE000EFE0	FULL	Peripheral Identification Register 0
CM7_SCS_PID1	0xE000EFE4	FULL	Peripheral Identification Register 1
CM7_SCS_PID2	0xE000EFE8	FULL	Peripheral Identification Register 2
CM7_SCS_PID3	0xE000EFEC	FULL	Peripheral Identification Register 3
CM7_SCS_CID0	0xE000EFF0	FULL	Component Identification Register 0
CM7_SCS_CID1	0xE000EFF4	FULL	Component Identification Register 1
CM7_SCS_CID2	0xE000EFF8	FULL	Component Identification Register 2
CM7_SCS_CID3	0xE000EFFC	FULL	Component Identification Register 3

4.5 ETM

Register Name	Address	Permission	Description
CM7_ETM_TRCPRGCTLR	0xE0041004	FULL	Programming Control Register
CM7_ETM_TRCSTATR	0xE004100C	FULL	Status Register
CM7_ETM_TRCCONFIGR	0xE0041010	FULL	Trace Configuration Register
CM7_ETM_TRCEVENTCTL0R	0xE0041020	FULL	Event Control 0 Register
CM7_ETM_TRCEVENTCTL1R	0xE0041024	FULL	Event Control 1 Register
CM7_ETM_TRCSTALLCTLR	0xE004102C	FULL	Stall Control Register
CM7_ETM_TRCTSTCLR	0xE0041030	FULL	Global Timestamp Control Register
CM7_ETM_TRCSYNCPR	0xE0041034	FULL	Synchronization Period Register
CM7_ETM_TRCCCCTLR	0xE0041038	FULL	Cycle Count Control Register
CM7_ETM_TRCTRACEIDR	0xE0041040	FULL	Trace ID Register
CM7_ETM_TRCVICTLR	0xE0041080	FULL	ViewInst Main Control Register
CM7_ETM_TRCVIPCSSCTLR	0xE004108C	FULL	ViewInst Start-Stop Processor Comparator Control Register
CM7_ETM_TRCCNTRLDVR	0xE0041140	FULL	Counter Reload Value Registers
CM7_ETM_TRCIDR8	0xE0041180	FULL	ID Register 8
CM7_ETM_TRCIDR9	0xE0041184	FULL	ID Register 9
CM7_ETM_TRCIDR10	0xE0041188	FULL	ID Register 10
CM7_ETM_TRCIDR11	0xE004118C	FULL	ID Register 11
CM7_ETM_TRCIDR12	0xE0041190	FULL	ID Register 12
CM7_ETM_TRCIDR13	0xE0041194	FULL	ID Register 13
CM7_ETM_TRCIMPSPEC0	0xE00411C0	FULL	Implementation Specific Register 0
CM7_ETM_TRCIDR0	0xE00411E0	FULL	ID Register 0
CM7_ETM_TRCIDR1	0xE00411E4	FULL	ID Register 1
CM7_ETM_TRCIDR2	0xE00411E8	FULL	ID Register 2
CM7_ETM_TRCIDR3	0xE00411EC	FULL	ID Register 3
CM7_ETM_TRCIDR4	0xE00411F0	FULL	ID Register 4
CM7_ETM_TRCIDR5	0xE00411F4	FULL	ID Register 5
CM7_ETM_TRCRSCTLR2	0xE0041208	FULL	Resource Selection Register 2
CM7_ETM_TRCRSCTLR3	0xE004120C	FULL	Resource Selection Register 3
CM7_ETM_TRCSSCCR0	0xE0041280	FULL	Single-shot Comparator Control Register 0
CM7_ETM_TRCSSCSR0	0xE00412A0	FULL	Single-shot Comparator Status Register 0
CM7_ETM_TRCSSPICR0	0xE00412C0	FULL	Single-shot Comparator Status Register 0
CM7_ETM_TRCOSLSR	0xE0041304	FULL	OS Lock Status Register
CM7_ETM_TRCPDCR	0xE0041310	FULL	Power Down Control Register
CM7_ETM_TRCPDSR	0xE0041314	FULL	Power Down Status Register
CM7_ETM_TRCITMISCOUTR	0xE0041ED0	FULL	Integration Miscellaneous Outputs Register
CM7_ETM_TRCITMISCINR	0xE0041EE0	FULL	Integration Miscellaneous Inputs Register
CM7_ETM_TRCITATBIDR	0xE0041EE4	FULL	Integration ATB Identification Register
CM7_ETM_TRCITDDATAR	0xE0041EE8	FULL	Integration Data ATB Data Register
CM7_ETM_TRCITIDATAR	0xE0041EEC	FULL	Integration Instruction ATB Data Register
CM7_ETM_TRCITDATBINR	0xE0041EF0	FULL	Integration Data ATB In Register
CM7_ETM_TRCITIATBINR	0xE0041EF4	FULL	Integration Instruction ATB In Register
CM7_ETM_TRCITDATBOUTR	0xE0041EF8	FULL	Integration Data ATB Out Register
CM7_ETM_TRCITIATBOUTR	0xE0041EFC	FULL	Integration Instruction ATB Out Register
CM7_ETM_TRCITCTRL	0xE0041F00	FULL	Integration Mode Control Register
CM7_ETM_TRCCLAIMSET	0xE0041FA0	FULL	Claim Tag Set Register
CM7_ETM_TRCCLAIMCLR	0xE0041FA4	FULL	Claim Tag Clear Register
CM7_ETM_TRCLAR	0xE0041FB0	FULL	Software Lock Access Register
CM7_ETM_TRCLSR	0xE0041FB4	FULL	Software Lock Status Register
CM7_ETM_TRCAUTHSTATUS	0xE0041FB8	FULL	Authentication Status Register
CM7_ETM_TRCDEVARCH	0xE0041FBC	FULL	Device Architecture Register

Register Name	Address	Permission	Description
CM7_ETM_TRCDEVID	0xE0041FC8	FULL	Device ID Register
CM7_ETM_TRCDEVTYPE	0xE0041FCC	FULL	CoreSight Device Type Register
CM7_ETM_PID4	0xE0041FD0	FULL	Peripheral Identification Register 4.
CM7_ETM_PID5	0xE0041FD4	FULL	Peripheral Identification Register 5.
CM7_ETM_PID6	0xE0041FD8	FULL	Peripheral Identification Register 6.
CM7_ETM_PID7	0xE0041FDC	FULL	Peripheral Identification Register 7.
CM7_ETM_PID0	0xE0041FE0	FULL	Peripheral Identification Register 0.
CM7_ETM_PID1	0xE0041FE4	FULL	Peripheral Identification Register 1.
CM7_ETM_PID2	0xE0041FE8	FULL	Peripheral Identification Register 2.
CM7_ETM_PID3	0xE0041FEC	FULL	Peripheral Identification Register 3.
CM7_ETM_CID0	0xE0041FF0	FULL	Component Identification Register 0.
CM7_ETM_CID1	0xE0041FF4	FULL	Component Identification Register 1.
CM7_ETM_CID2	0xE0041FF8	FULL	Component Identification Register 2.
CM7_ETM_CID3	0xE0041FFC	FULL	Component Identification Register 3.

4.6 CM7CTI

Register Name	Address	Permission	Description
CM7_CM7CTI_CTICONTROL	0xE0042000	FULL	CTI Control Register
CM7_CM7CTI_CTIINTACK	0xE0042010	FULL	CTI Interrupt Acknowledge Register
CM7_CM7CTI_CTIAPPSET	0xE0042014	FULL	CTI Application Trigger Set Register
CM7_CM7CTI_CTIAPPCLEAR	0xE0042018	FULL	CTI Application Trigger Clear Register
CM7_CM7CTI_CTIAPPULSE	0xE004201C	FULL	CTI Application Pulse Register
CM7_CM7CTI_CTIINEN0	0xE0042020	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN1	0xE0042024	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN2	0xE0042028	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN3	0xE004202C	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN4	0xE0042030	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN5	0xE0042034	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN6	0xE0042038	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIINEN7	0xE004203C	FULL	CTI Trigger to Channel Enable Registers
CM7_CM7CTI_CTIOUTEN0	0xE00420A0	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN1	0xE00420A4	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN2	0xE00420A8	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN3	0xE00420AC	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN4	0xE00420B0	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN5	0xE00420B4	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN6	0xE00420B8	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTIOUTEN7	0xE00420BC	FULL	CTI Channel to Trigger Enable Registers
CM7_CM7CTI_CTITRIGINSTATUS	0xE0042130	FULL	CTI Trigger In Status Register
CM7_CM7CTI_CTITRIGOUTSTATUS	0xE0042134	FULL	CTI Trigger Out Status Register
CM7_CM7CTI_CTICHINSTATUS	0xE0042138	FULL	CTI Channel In Status Register
CM7_CM7CTI_CTICHOUTSTATUS	0xE004213C	FULL	CTI Channel Out Status Register
CM7_CM7CTI_CTIGATE	0xE0042140	FULL	Enable CTI Channel Gate Register
CM7_CM7CTI_ASICCTL	0xE0042144	FULL	External Multiplexor Control Register
CM7_CM7CTI_ITCHINACK	0xE0042EDC	FULL	ITCHINACK Register
CM7_CM7CTI_ITTRIGINACK	0xE0042EE0	FULL	ITTRIGINACK Register
CM7_CM7CTI_ITCHOUT	0xE0042EE4	FULL	ITCHOUT Register
CM7_CM7CTI_ITTRIGOUT	0xE0042EE8	FULL	ITTRIGOUT Register
CM7_CM7CTI_ITCHOUTACK	0xE0042EEC	FULL	ITCHOUTACK Register
CM7_CM7CTI_ITTRIGOUTACK	0xE0042EF0	FULL	ITTRIGOUTACK Register
CM7_CM7CTI_ITCHIN	0xE0042EF4	FULL	ITCHIN Register
CM7_CM7CTI_ITTRIGIN	0xE0042EF8	FULL	ITTRIGIN Register
CM7_CM7CTI_ITCTRL	0xE0042F00	FULL	Integration Mode Control Register
CM7_CM7CTI_CLAIMSET	0xE0042FA0	FULL	Claim Tag Set Register
CM7_CM7CTI_CLAIMCLR	0xE0042FA4	FULL	Claim Tag Clear Register
CM7_CM7CTI_LOCKACCESS	0xE0042FB0	FULL	Lock Access Register
CM7_CM7CTI_LOCKSTATUS	0xE0042FB4	FULL	Lock Status Register
CM7_CM7CTI_AUTHSTATUS	0xE0042FB8	FULL	Authentication Status Register
CM7_CM7CTI_DEVID	0xE0042FC8	FULL	Device Configuration Register
CM7_CM7CTI_DEVTYPE	0xE0042FCC	FULL	Device Type Identifier Register
CM7_CM7CTI_PID4	0xE0042FD0	FULL	Peripheral Identification Register 4
CM7_CM7CTI_PID5	0xE0042FD4	FULL	Peripheral Identification Register 5
CM7_CM7CTI_PID6	0xE0042FD8	FULL	Peripheral Identification Register 6

Register Name	Address	Permission	Description
CM7_CM7CTI_PID7	0xE0042FDC	FULL	Peripheral Identification Register 7
CM7_CM7CTI_PID0	0xE0042FE0	FULL	Peripheral Identification Register 0
CM7_CM7CTI_PID1	0xE0042FE4	FULL	Peripheral Identification Register 1
CM7_CM7CTI_PID2	0xE0042FE8	FULL	Peripheral Identification Register 2
CM7_CM7CTI_PID3	0xE0042FEC	FULL	Peripheral Identification Register 3
CM7_CM7CTI_CID0	0xE0042FF0	FULL	Component Identification Register 0
CM7_CM7CTI_CID1	0xE0042FF4	FULL	Component Identification Register 1
CM7_CM7CTI_CID2	0xE0042FF8	FULL	Component Identification Register 2
CM7_CM7CTI_CID3	0xE0042FFC	FULL	Component Identification Register 3

4.7 TRCCTI

Register Name	Address	Permission	Description
CM7_TRCCTI_CTICONTROL	0xE0080000	FULL	CTI Control Register
CM7_TRCCTI_CTIINTACK	0xE0080010	FULL	CTI Interrupt Acknowledge Register
CM7_TRCCTI_CTIAPPSET	0xE0080014	FULL	CTI Application Trigger Set Register
CM7_TRCCTI_CTIAPPCLEAR	0xE0080018	FULL	CTI Application Trigger Clear Register
CM7_TRCCTI_CTIAPPULSE	0xE008001C	FULL	CTI Application Pulse Register
CM7_TRCCTI_CTIENEN0	0xE0080020	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN1	0xE0080024	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN2	0xE0080028	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN3	0xE008002C	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN4	0xE0080030	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN5	0xE0080034	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN6	0xE0080038	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIENEN7	0xE008003C	FULL	CTI Trigger to Channel Enable Registers
CM7_TRCCTI_CTIOUTEN0	0xE00800A0	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN1	0xE00800A4	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN2	0xE00800A8	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN3	0xE00800AC	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN4	0xE00800B0	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN5	0xE00800B4	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN6	0xE00800B8	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTIOUTEN7	0xE00800BC	FULL	CTI Channel to Trigger Enable Registers
CM7_TRCCTI_CTITRIGINSTATUS	0xE0080130	FULL	CTI Trigger In Status Register
CM7_TRCCTI_CTITRIGOUTSTATUS	0xE0080134	FULL	CTI Trigger Out Status Register
CM7_TRCCTI_CTICHINSTATUS	0xE0080138	FULL	CTI Channel In Status Register
CM7_TRCCTI_CTICHOUTSTATUS	0xE008013C	FULL	CTI Channel Out Status Register
CM7_TRCCTI_CTIGATE	0xE0080140	FULL	Enable CTI Channel Gate Register
CM7_TRCCTI_ASICCTL	0xE0080144	FULL	External Multiplexor Control Register
CM7_TRCCTI_ITCHINACK	0xE0080EDC	FULL	ITCHINACK Register
CM7_TRCCTI_ITTRIGINACK	0xE0080EE0	FULL	ITTRIGINACK Register
CM7_TRCCTI_ITCHOUT	0xE0080EE4	FULL	ITCHOUT Register
CM7_TRCCTI_ITTRIGOUT	0xE0080EE8	FULL	ITTRIGOUT Register
CM7_TRCCTI_ITCHOUTACK	0xE0080EEC	FULL	ITCHOUTACK Register
CM7_TRCCTI_ITTRIGOUTACK	0xE0080EF0	FULL	ITTRIGOUTACK Register
CM7_TRCCTI_ITCHIN	0xE0080EF4	FULL	ITCHIN Register
CM7_TRCCTI_ITTRIGIN	0xE0080EF8	FULL	ITTRIGIN Register
CM7_TRCCTI_ITCTRL	0xE0080F00	FULL	Integration Mode Control Register
CM7_TRCCTI_CLAIMSET	0xE0080FA0	FULL	Claim Tag Set Register
CM7_TRCCTI_CLAIMCLR	0xE0080FA4	FULL	Claim Tag Clear Register
CM7_TRCCTI_LOCKACCESS	0xE0080FB0	FULL	Lock Access Register
CM7_TRCCTI_LOCKSTATUS	0xE0080FB4	FULL	Lock Status Register
CM7_TRCCTI_AUTHSTATUS	0xE0080FB8	FULL	Authentication Status Register
CM7_TRCCTI_DEVID	0xE0080FC8	FULL	Device Configuration Register
CM7_TRCCTI_DEVTYPE	0xE0080FCC	FULL	Device Type Identifier Register
CM7_TRCCTI_PID4	0xE0080FD0	FULL	Peripheral Identification Register 4
CM7_TRCCTI_PID5	0xE0080FD4	FULL	Peripheral Identification Register 5
CM7_TRCCTI_PID6	0xE0080FD8	FULL	Peripheral Identification Register 6
CM7_TRCCTI_PID7	0xE0080FDC	FULL	Peripheral Identification Register 7
CM7_TRCCTI_PID0	0xE0080FE0	FULL	Peripheral Identification Register 0
CM7_TRCCTI_PID1	0xE0080FE4	FULL	Peripheral Identification Register 1
CM7_TRCCTI_PID2	0xE0080FE8	FULL	Peripheral Identification Register 2
CM7_TRCCTI_PID3	0xE0080FEC	FULL	Peripheral Identification Register 3

Register Name	Address	Permission	Description
CM7_TRCCTI_CID0	0xE0080FF0	FULL	Component Identification Register 0
CM7_TRCCTI_CID1	0xE0080FF4	FULL	Component Identification Register 1
CM7_TRCCTI_CID2	0xE0080FF8	FULL	Component Identification Register 2
CM7_TRCCTI_CID3	0xE0080FFC	FULL	Component Identification Register 3

4.8 ETB_CSTF

4.8.1 TRC_CSTF

Register Name	Address	Permission	Description
CM7_ETB_CSTF_CSTFCTL	0xE008C000	FULL	Funnel Control Register
CM7_ETB_CSTF_CSTFPCTL	0xE008C004	FULL	Priority Control Register
CM7_ETB_CSTF_ITATBDATA0	0xE008CEE0	FULL	Integration Register
CM7_ETB_CSTF_ITATBCTR2	0xE008CEFC	FULL	Integration Register
CM7_ETB_CSTF_ITATBCTR1	0xE008CEFA	FULL	Integration Register
CM7_ETB_CSTF_ITATBCTR0	0xE008CEF8	FULL	Integration Register
CM7_ETB_CSTF_ITCTRL	0xE008CF00	FULL	Integration Mode Control Register
CM7_ETB_CSTF_CLAIMSET	0xE008CFA0	FULL	Claim Tag Set Register
CM7_ETB_CSTF_CLAIMCLR	0xE008CFA4	FULL	Claim Tag Clear Register
CM7_ETB_CSTF_LOCKACCESS	0xE008CFB0	FULL	Lock Access Register
CM7_ETB_CSTF_LOCKSTATUS	0xE008CFB4	FULL	Lock Status Register
CM7_ETB_CSTF_AUTHSTATUS	0xE008CFB8	FULL	Authentication Status Register
CM7_ETB_CSTF_DEVID	0xE008CFC8	FULL	Device ID
CM7_ETB_CSTF_DEVTYPE	0xE008CFC0	FULL	Device Type Identifier Register
CM7_ETB_CSTF_PID4	0xE008CFD0	FULL	Peripheral Identification Register 4
CM7_ETB_CSTF_PID5	0xE008CFD4	FULL	Peripheral Identification Register 5
CM7_ETB_CSTF_PID6	0xE008CFD8	FULL	Peripheral Identification Register 6
CM7_ETB_CSTF_PID7	0xE008CFDC	FULL	Peripheral Identification Register 7
CM7_ETB_CSTF_PID0	0xE008CFE0	FULL	Peripheral Identification Register 0
CM7_ETB_CSTF_PID1	0xE008CFE4	FULL	Peripheral Identification Register 1
CM7_ETB_CSTF_PID2	0xE008CFE8	FULL	Peripheral Identification Register 2
CM7_ETB_CSTF_PID3	0xE008CFEC	FULL	Peripheral Identification Register 3
CM7_ETB_CSTF_CID0	0xE008CFF0	FULL	Component Identification Register 0
CM7_ETB_CSTF_CID1	0xE008CFF4	FULL	Component Identification Register 1
CM7_ETB_CSTF_CID2	0xE008CFF8	FULL	Component Identification Register 2
CM7_ETB_CSTF_CID3	0xE008CFFC	FULL	Component Identification Register 3

4.9 ETB

Register Name	Address	Permission	Description
CM7_ETB_ETBRDP	0xE008D004	FULL	RAM Depth Register
CM7_ETB_ETBSTS	0xE008D00C	FULL	Status Register
CM7_ETB_ETBRRD	0xE008D010	FULL	RAM Read Data Register
CM7_ETB_ETBRRP	0xE008D014	FULL	RAM Read Pointer Register
CM7_ETB_ETBRWP	0xE008D018	FULL	RAM Write Pointer Register
CM7_ETB_ETBTRG	0xE008D01C	FULL	Trigger Counter Register
CM7_ETB_ETBCTL	0xE008D020	FULL	Control Register
CM7_ETB_ETBRWD	0xE008D024	FULL	RAM Write Data Register
CM7_ETB_ETBFFSR	0xE008D300	FULL	Formatter and Flush Status Register
CM7_ETB_ETBFFCR	0xE008D304	FULL	Formatter and Flush Control Register
CM7_ETB_ITMISCOP0	0xE008DEE0	FULL	Integration Register
CM7_ETB_ITTRFLINACK	0xE008DEE4	FULL	Integration Register
CM7_ETB_ITTRFLIN	0xE008DEE8	FULL	Integration Register
CM7_ETB_ITATBDATA0	0xE008DEEC	FULL	Integration Register
CM7_ETB_ITATBCTR2	0xE008DEF0	FULL	Integration Register
CM7_ETB_ITATBCTR1	0xE008DEF4	FULL	Integration Register
CM7_ETB_ITATBCTR0	0xE008DEF8	FULL	Integration Register
CM7_ETB_ITCTRL	0xE008DF00	FULL	Integration Mode Control Register
CM7_ETB_CLAIMSET	0xE008DFA0	FULL	Claim Tag Set Register
CM7_ETB_CLAIMCLR	0xE008DFA4	FULL	Claim Tag Clear Register
CM7_ETB_LOCKACCESS	0xE008DFB0	FULL	Lock Access Register
CM7_ETB_LOCKSTATUS	0xE008DFB4	FULL	Lock Status Register
CM7_ETB_AUTHSTATUS	0xE008DFB8	FULL	Authentication Status Register
CM7_ETB_DEVID	0xE008DFC8	FULL	Device ID
CM7_ETB_DEVTYPE	0xE008DFC0	FULL	Device Type Identifier Register

Register Name	Address	Permission	Description
CM7_ETB_PID4	0xE008DFD0	FULL	Peripheral Identification Register 4
CM7_ETB_PID5	0xE008DFD4	FULL	Peripheral Identification Register 5
CM7_ETB_PID6	0xE008DFD8	FULL	Peripheral Identification Register 6
CM7_ETB_PID7	0xE008DFDC	FULL	Peripheral Identification Register 7
CM7_ETB_PID0	0xE008DFE0	FULL	Peripheral Identification Register 0
CM7_ETB_PID1	0xE008DFE4	FULL	Peripheral Identification Register 1
CM7_ETB_PID2	0xE008DFE8	FULL	Peripheral Identification Register 2
CM7_ETB_PID3	0xE008DFEC	FULL	Peripheral Identification Register 3
CM7_ETB_CID0	0xE008DFF0	FULL	Component Identification Register 0
CM7_ETB_CID1	0xE008DFF4	FULL	Component Identification Register 1
CM7_ETB_CID2	0xE008DFF8	FULL	Component Identification Register 2
CM7_ETB_CID3	0xE008DFFC	FULL	Component Identification Register 3

4.10 TPIU

Register Name	Address	Permission	Description
CM7_TPIU_TPIU_SPSR	0xE008E000	FULL	Supported Port Size Register
CM7_TPIU_TPIU_CPSR	0xE008E004	FULL	Current Port Size Register
CM7_TPIU_TPIU_STMR	0xE008E100	FULL	Supported Trigger Modes Register
CM7_TPIU_TPIU_TCVR	0xE008E104	FULL	Trigger Counter Value Register
CM7_TPIU_TPIU_TMR	0xE008E108	FULL	Trigger Multiplier register
CM7_TPIU_TPIU_STPMR	0xE008E200	FULL	Supported Test Patterns/Modes register
CM7_TPIU_TPIU_CTPMR	0xE008E204	FULL	Current Test Pattern/Modes register
CM7_TPIU_TPIU_TPRCR	0xE008E208	FULL	TPIU Test Pattern Repeat Counter Register
CM7_TPIU_TPIU_FFSR	0xE008E300	FULL	Formatter and Flush Status Register
CM7_TPIU_TPIU_FFCR	0xE008E304	FULL	Formatter and Flush Control Register
CM7_TPIU_TPIU_FSCR	0xE008E308	FULL	Formatter Synchronization Counter Register
CM7_TPIU_TPIU_EXCTLIPR	0xE008E400	FULL	TPIU EXCTL In Port Register
CM7_TPIU_TPIU_EXCTLOPR	0xE008E404	FULL	TPIU EXCTL Out Port register
CM7_TPIU_ITTRFLINACK	0xE008EEE4	FULL	Integration Test Trigger In and Flush In Acknowledge register
CM7_TPIU_ITTRFLIN	0xE008EEE8	FULL	Integration Test Trigger In and Flush In register
CM7_TPIU_ITATBDATA0	0xE008EEEC	FULL	Integration Test ATB Data register 0
CM7_TPIU_ITATBCTR2	0xE008EEF0	FULL	Integration Test ATB Control Register 2
CM7_TPIU_ITATBCTR1	0xE008EEF4	FULL	Integration Test ATB Control Register 1
CM7_TPIU_ITATBCTR0	0xE008EEF8	FULL	Integration Test ATB Control Register 0
CM7_TPIU_ITCTRL	0xE008EF00	FULL	Integration Mode Control register
CM7_TPIU_CLAIMSET	0xE008EFA0	FULL	Claim Tag Set Register
CM7_TPIU_CLAIMCLR	0xE008EFA4	FULL	Claim Tag Clear Register
CM7_TPIU_LOCKACCESS	0xE008EFB0	FULL	Lock Access Register
CM7_TPIU_LOCKSTATUS	0xE008EFB4	FULL	Lock Status Register
CM7_TPIU_AUTHSTATUS	0xE008EFB8	FULL	Authentication Status register
CM7_TPIU_DEVID	0xE008EFC8	FULL	Device Configuration register
CM7_TPIU_DEVTYPE	0xE008EFC0	FULL	Device Type Identifier register
CM7_TPIU_PID4	0xE008EFD0	FULL	Peripheral Identification Register 4
CM7_TPIU_PID0	0xE008EFE0	FULL	Peripheral Identification Register 0
CM7_TPIU_PID1	0xE008EFE4	FULL	Peripheral Identification Register 1
CM7_TPIU_PID2	0xE008EFE8	FULL	Peripheral Identification Register 2
CM7_TPIU_PID3	0xE008EFEC	FULL	Peripheral Identification Register 3
CM7_TPIU_CID0	0xE008EFF0	FULL	Component Identification Register 0
CM7_TPIU_CID1	0xE008EFF4	FULL	Component Identification Register 1
CM7_TPIU_CID2	0xE008EFF8	FULL	Component Identification Register 2
CM7_TPIU_CID3	0xE008EFFC	FULL	Component Identification Register 3

4.11 ROMTABLE

Register Name	Address	Permission	Description
CM7_ROMTABLE_TRC_CT1	0xE00BF000	FULL	CM7 CoreSight ROM Table Peripheral #0
CM7_ROMTABLE_TRC_TRC_CSTF	0xE00BF004	FULL	CM7 CoreSight ROM Table Peripheral #1
CM7_ROMTABLE_TRC_ETB	0xE00BF008	FULL	CM7 CoreSight ROM Table Peripheral #2
CM7_ROMTABLE_TRC_TPIU	0xE00BF00C	FULL	CM7 CoreSight ROM Table Peripheral #3
CM7_ROMTABLE_TRC_CSMT	0xE00BFFC0	FULL	CM7 CoreSight ROM Table Memory Type
CM7_ROMTABLE_TRC_PID4	0xE00BFFD0	FULL	CM7 CoreSight ROM Table Peripheral ID #4
CM7_ROMTABLE_TRC_PID0	0xE00BFFE0	FULL	CM7 CoreSight ROM Table Peripheral ID #0

Register Name	Address	Permission	Description
CM7_ROMTABLE_TRC_PID1	0xE00BFFE4	FULL	CM7 CoreSight ROM Table Peripheral ID #1
CM7_ROMTABLE_TRC_PID2	0xE00BFFE8	FULL	CM7 CoreSight ROM Table Peripheral ID #2
CM7_ROMTABLE_TRC_PID3	0xE00BFFEC	FULL	CM7 CoreSight ROM Table Peripheral ID #3
CM7_ROMTABLE_TRC_CID0	0xE00BFFF0	FULL	CM7 CoreSight ROM Table Component ID #0
CM7_ROMTABLE_TRC_CID1	0xE00BFFF4	FULL	CM7 CoreSight ROM Table Component ID #1
CM7_ROMTABLE_TRC_CID2	0xE00BFFF8	FULL	CM7 CoreSight ROM Table Component ID #2
CM7_ROMTABLE_TRC_CID3	0xE00BFFF0	FULL	CM7 CoreSight ROM Table Component ID #3

4.12 ROMTABLE

Register Name	Address	Permission	Description
CM7_ROMTABLE_CM7	0xE00FE000	FULL	CM7 CoreSight ROM Table Peripheral #0
CM7_ROMTABLE_CM7_ETM	0xE00FE004	FULL	CM7 CoreSight ROM Table Peripheral #1
CM7_ROMTABLE_CM7_CTI	0xE00FE008	FULL	CM7 CoreSight ROM Table Peripheral #2
CM7_ROMTABLE_DBG_TRC_ROM	0xE00FE010	FULL	CM7 CoreSight ROM Table Peripheral #3
CM7_ROMTABLE_CSMT	0xE00FEFC0	FULL	CM7 CoreSight ROM Table Memory Type
CM7_ROMTABLE_PID4	0xE00FEFD0	FULL	CM7 CoreSight ROM Table Peripheral ID #4
CM7_ROMTABLE_PID0	0xE00FEFE0	FULL	CM7 CoreSight ROM Table Peripheral ID #0
CM7_ROMTABLE_PID1	0xE00FEFE4	FULL	CM7 CoreSight ROM Table Peripheral ID #1
CM7_ROMTABLE_PID2	0xE00FEFE8	FULL	CM7 CoreSight ROM Table Peripheral ID #2
CM7_ROMTABLE_PID3	0xE00FEFEC	FULL	CM7 CoreSight ROM Table Peripheral ID #3
CM7_ROMTABLE_CID0	0xE00FEFF0	FULL	CM7 CoreSight ROM Table Component ID #0
CM7_ROMTABLE_CID1	0xE00FEFF4	FULL	CM7 CoreSight ROM Table Component ID #1
CM7_ROMTABLE_CID2	0xE00FEFF8	FULL	CM7 CoreSight ROM Table Component ID #2
CM7_ROMTABLE_CID3	0xE00FEFF0	FULL	CM7 CoreSight ROM Table Component ID #3

4.13 ROM

Register Name	Address	Permission	Description
CM7_ROM_SCS	0xE00FF000	FULL	CM7 CoreSight ROM Table Peripheral #0
CM7_ROM_DWT	0xE00FF004	FULL	CM7 CoreSight ROM Table Peripheral #1
CM7_ROM_FPB	0xE00FF008	FULL	CM7 CoreSight ROM Table Peripheral #2
CM7_ROM_ITM	0xE00FF00C	FULL	CM7 CoreSight ROM Table Peripheral #3
CM7_ROM_CSMT	0xE00FFFC0	FULL	CM7 CoreSight ROM Table Memory Type
CM7_ROM_PID4	0xE00FFFD0	FULL	CM7 CoreSight ROM Table Peripheral ID #4
CM7_ROM_PID0	0xE00FFFE0	FULL	CM7 CoreSight ROM Table Peripheral ID #0
CM7_ROM_PID1	0xE00FFFE4	FULL	CM7 CoreSight ROM Table Peripheral ID #1
CM7_ROM_PID2	0xE00FFFE8	FULL	CM7 CoreSight ROM Table Peripheral ID #2
CM7_ROM_PID3	0xE00FFFE0	FULL	CM7 CoreSight ROM Table Peripheral ID #3
CM7_ROM_CID0	0xE00FFFF0	FULL	CM7 CoreSight ROM Table Component ID #0
CM7_ROM_CID1	0xE00FFFF4	FULL	CM7 CoreSight ROM Table Component ID #1
CM7_ROM_CID2	0xE00FFFF8	FULL	CM7 CoreSight ROM Table Component ID #2
CM7_ROM_CID3	0xE00FFFF0	FULL	CM7 CoreSight ROM Table Component ID #3

4.14 Register Details

4.14.1 ITM

4.14.1.1 CM7_ITM_STIM

Description: Stimulus Port registers

Address: 0xE0000000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: The ITM_STIMx register characteristics are:

Purpose: Provide the interface for generating instrumentation messages.

Usage constraints:

- Accessible by word-aligned byte, halfword, and word accesses.
- The number of ITM_STIM registers is an IMPLEMENTATION DEFINED multiple of eight, see Trace Privilege Register, ITM_TPR on page C1-775.
- When DEMCR.TRCENA is 0, the ITM_STIM registers are UNKNOWN on reads and ignore writes.

Configurations: Always implemented.

Attributes: See Table C1-11 on page C1-773, and the register field descriptions. The address of ITM_STIMn is (0xE0000000 + 4n).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STIMULUS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	STIMULUS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	STIMULUS [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	STIMULUS [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	STIMULUS	RW	RW	X	Data write to the stimulus port FIFO, for forwarding as a software event packet. When read, bit[0] indicates whether the stimulus port FIFO can accept data: 0: Stimulus port FIFO full. 1: Stimulus port FIFO can accept at least one word. This bit is UNKNOWN after a Power-on reset.

4.14.1.2 CM7_ITM_TER

Description: Trace Enable Register

Address: 0xE0000E00

Offset: 0xE00

Retention: Retained

IsDeepSleep: No

Comment: The ITM_TERx characteristics are:

Purpose: Provide an individual enable bit for each ITM_STIM register.

Usage constraints

- Each ITM_TER provides enable bits for 32 ITM_STIM registers.

- Bits corresponding to unimplemented ITM_STIM registers are RAZ/WI. See Trace Privilege Register, ITM_TPR on page C1-775 for information about the number of implemented ITM_STIM registers.

- The processor ignores any unprivileged write to an ITM_TERx bit if the corresponding ITM_TPR.PRIVMASK bit is set to 1, see Trace Privilege Register, ITM_TPR on page C1-775. Configurations: Always implemented.

Attributes: See Table C1-11 on page C1-773.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STIMENA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	STIMENA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	STIMENA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	STIMENA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	STIMENA	RW	RW	0	For bit STIMENA[n]: 0: Stimulus port (n) disabled 1: Stimulus port (n) enabled

4.14.1.3 CM7_ITM_TPR

Description: ITM Trace Privilege Register
Address: 0xE0000E40
Offset: 0xE40
Retention: Retained
IsDeepSleep: No
Comment: Characteristics and bit assignments of the ITM_TPR register.
 Purpose: Enables an operating system to control the stimulus ports that are accessible by user code.
 Usage constraints: You can only write to this register in privileged mode.
 Configurations: This register is available if the ITM is configured in your implementation.
 Attributes: Refer to the ITM register summary table.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				PRIVMASK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PRIVMASK	RW	RW	0	Bit mask to enable tracing on ITM stimulus ports: bit [0] = stimulus ports [7:0] bit [1] = stimulus ports [15:8] bit [2] = stimulus ports [23:16] bit [3] = stimulus ports [31:24]

4.14.1.4 CM7_ITM_TCR

Description: Trace Control Register
Address: 0xE0000E80
Offset: 0xE80
Retention: Retained
IsDeepSleep: No
Comment: The ITM_TCR characteristics are:
 Purpose: Configures and controls transfers through the ITM interface.
 Usage constraints: For information about constraints that apply in a system that supports multiple trace streams see CoreSight requirements for the TraceBusID field on page C1-778.
 Configurations: Always implemented.
 Attributes: See Table C1-11 on page C1-773, and the register field descriptions.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SWOENA [4:4]	TXENA [3:3]	SYNCENA [2:2]	TSENA [1:1]	ITMENA [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				GTSFREQ [11:10]		TSPRESCALE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	BUSY [23:23]	TRACEBUSID [22:16]						

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ITMENA	RW	RW	0	Enables the ITM: 0 Disabled. 1 Enabled. This is the master enable for the ITM unit. A debugger must set this bit to 1 to permit writes to all Stimulus Port registers. A Power-on reset clears this bit to 0.
1	TSENA	RW	RW	0	Enables Local timestamp generation: 0 Disabled. 1 Enabled. A Power-on reset clears this bit to 0.
2	SYNCENA	RW	RW	0	Enables Synchronization packet transmission for a synchronous TPIU: 0 Disabled. 1 Enabled. A Power-on reset clears this bit to 0. Note: If a debugger sets this bit to 1 it must also configure DWT_CTRL.SYNCTAP for the correct synchronization speed, see Control register, DWT_CTRL on page C1-797.

Bits	Name	SW	HW	Default or Enum	Description
3	TXENA	RW	RW	0	Enables forwarding of hardware event packet from the DWT unit to the ITM for output to the TPIU: 0 Disabled. 1 Enabled. It is IMPLEMENTATION DEFINED whether the DWT discards packets that it cannot forward to the ITM. Note: If a debugger changes this bit from 0 to 1, the DWT might forward a hardware event packet that it has previously generated. A Power-on reset clears this bit to 0.
4	SWOENA	RW	RW	0	Enables asynchronous clocking of the timestamp counter: 0 Timestamp counter uses the processor system clock. 1 Timestamp counter uses asynchronous clock from the TPIU interface. The timestamp counter is held in reset while the output line is idle. Which clocking modes are implemented is IMPLEMENTATION DEFINED. If the implementation does not support both modes this bit is either RAZ or RAO, to indicate the implemented mode. When this is a RW bit, on a Power-on reset, the value of this bit is UNKNOWN
8:9	TSPRESCALE	RW	RW	0	Local timestamp prescaler, used with the trace packet reference clock. The possible values are: 00 No prescaling. 01 Divide by 4. 10 Divide by 16. 11 Divide by 64. If implemented, a Power-on reset clears this field to zero. If the processor does not implement the timestamp prescaler then these bits are reserved, RAZ/WI.
10:11	GTSFREQ	RW	RW	0	Global timestamp frequency. Defines how often the ITM generates a global timestamp, based on the global timestamp clock frequency, or disables generation of global timestamps. The possible values are: 00 Disable generation of global timestamps. 01 Generate timestamp request whenever the ITM detects a change in global timestamp counter bits[47:7]. This is approximately every 128 cycles. 10 Generate timestamp request whenever the ITM detects a change in global timestamp counter bits[47:13]. This is approximately every 8192 cycles. 11 Generate a timestamp after every packet, if the output FIFO is empty. For more information see Global timestamping on page C1-771. A Power-on reset clears this field to zero. If the implementation does not support global timestamping then these bits are reserved, RAZ/WI.
16:22	TRACEBUSID	RW	RW	0	Identifier for multi-source trace stream formatting. If multi-source trace is in use, the debugger must write a non-zero value to this field. For more information see CoreSight requirements for the TraceBusID field on page C1-778. On a Power-on reset, the value of this field is UNKNOWN.

Bits	Name	SW	HW	Default or Enum	Description
23	BUSY	RW	RW	0	Indicates whether the ITM is currently processing events: 0 ITM is not processing any events. 1 ITM events present and being drained. These bits are read-only.

4.14.1.5 CM7_ITM_ITATRDR

Description: Integration Mode Read ATB Ready
Address: 0xE0000EF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.1.6 CM7_ITM_ITATVAL

Description: Integration Mode Write ATB Valid
Address: 0xE0000EF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	N/A

4.14.1.7 CM7_ITM_TCTRL

Description: Integration Mode Control Register
Address: 0xE0000F00
Offset: 0xF00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	N/A

4.14.1.8 CM7_ITM_LAR

Description: Lock Access Register
Address: 0xE0000FB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	N/A

4.14.1.9 CM7_ITM_LSR

Description: Lock Status Register
Address: 0xE0000FB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.1.10 CM7_ITM_PID4

Description: Peripheral Identification Register 4.
Address: 0xE0000FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.1.11 CM7_ITM_PID5

Description: Peripheral Identification Register 5.
Address: 0xE0000FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.1.12 CM7_ITM_PID6

Description: Peripheral Identification Register 6.
Address: 0xE0000FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.1.13 CM7_ITM_PID7

Description: Peripheral Identification Register 7.
Address: 0xE0000FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.1.14 CM7_ITM_PID0

Description: Peripheral Identification Register 0.
Address: 0xE0000FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	N/A

4.14.1.15 CM7_ITM_PID1

Description: Peripheral Identification Register 1.
Address: 0xE0000FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	N/A

4.14.1.16 CM7_ITM_PID2

Description: Peripheral Identification Register 2.
Address: 0xE0000FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	N/A

4.14.1.17 CM7_ITM_PID3

Description: Peripheral Identification Register 3.
Address: 0xE0000FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision

4.14.1.18 CM7_ITM_CID0

Description: Component Identification Register 0.
Address: 0xE0000FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.1.19 CM7_ITM_CID1

Description: Component Identification Register 1.
Address: 0xE0000FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	N/A

4.14.1.20 CM7_ITM_CID2

Description: Component Identification Register 2.
Address: 0xE0000FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.1.21 CM7_ITM_CID3

Description: Component Identification Register 3.
Address: 0xE0000FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.2 DWT

4.14.2.1 CM7_DWT_CTRL

Description: Control register

Address: 0xE0001000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: The CTRL register characteristics are:
 Purpose: Provides configuration and status information for the DWT unit, and used to control features of the unit.
 Usage constraints: There are no usage constraints.
 Configurations: Always implemented.
 Attributes: See Table C1-21 and the register field descriptions.

Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name				POSTPRESET [4:1]				CYCCNTENA [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PCSAMPLENA [12:12]	SYNCTAP [11:10]		CYCTAP [9:9]	POSTINIT [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	CYCEVTENA [22:22]	FOLDEVTENA [21:21]	LSUEVTENA [20:20]	SLEEPEVTENA [19:19]	EXCEVTENA [18:18]	CPIEVTENA [17:17]	EXCTRCENA [16:16]

Bits	31	30	29	28	27	26	25	24
Name	NUMCOMP [31:28]				NOTRCPKT [27:27]	NOEXTTRIG [26:26]	NOCYCCNT [25:25]	NOPRFCNT [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CYCCNTENA	RW	RW	0	Enables CYCCNT: 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOCYCCNT bit is RAO.
1:4	POSTPRESET	RW	RW	0	Reload value for the POSTCNT counter. For more information see The POSTCNT timer on page C1-792. This field is UNK/SBZP if the NOCYCCNT bit is RAO.
5:8	POSTINIT	RW	RW	0	Initial value for the POSTCNT counter. For more information see Enabling POSTCNT, and behavior of accesses to the DWT_CTRL.POSTINIT field and The POSTCNT timer on page C1-792. This field is UNK/SBZP if the NOCYCCNT bit is RAO. Note This field was previously called POSTCNT. The changed name gives a better indication of its function.
9	CYCTAP	RW	RW	0	Selects the position of the POSTCNT tap on the CYCCNT counter: 0 POSTCNT tap at CYCCNT[6]. 1 POSTCNT tap at CYCCNT[10]. For more information see The POSTCNT timer on page C1-792. This bit is UNK/SBZP if the NOCYCCNT bit is RAO.

Bits	Name	SW	HW	Default or Enum	Description
10:11	SYNCTAP	RW	RW	0	Selects the position of the synchronization packet counter tap on the CYCCNT counter. This determines the Synchronization packet rate: 00 Disabled. No Synchronization packets. 01 Synchronization counter tap at CYCCNT[24]. 10 Synchronization counter tap at CYCCNT[26]. 11 Synchronization counter tap at CYCCNT[28]. For more information see The synchronization packet timer on page C1-794. This field is UNK/SBZP if the NOCYCCNT bit is RAO.
12	PCSAMPLENA	RW	RW	0	Enables use of POSTCNT counter as a timer for Periodic PC sample packet generation: 0 No Periodic PC sample packets generated. 1 Periodic PC sample packets generated. See The POSTCNT timer on page C1-792 for more information. This bit is UNK/SBZP if the NOTRCPKT bit is RAO or the NOCYCCNT bit is RAO.
16	EXCTRCENA	RW	RW	0	Enables generation of exception trace: 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOTRCPKT bit is RAO.
17	CPIEVTENA	RW	RW	0	Enables generation of the CPI counter overflow event: 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOPRFCNT bit is RAO.
18	EXCEVTENA	RW	RW	0	Enables generation of the Exception overhead counter overflow event: 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOPRFCNT bit is RAO.
19	SLEEPEVTENA	RW	RW	0	Enables generation of the Sleep counter overflow event. 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOPRFCNT bit is RAO.
20	LSUEVTENA	RW	RW	0	Enables generation of the LSU counter overflow event. 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOPRFCNT bit is RAO.
21	FOLDEVTENA	RW	RW	0	Enables generation of the Folded-instruction counter overflow event: 0 Disabled. 1 Enabled. This bit is UNK/SBZP if the NOPRFCNT bit is RAO.
22	CYCEVTENA	RW	RW	0	Enables POSTCNT underflow Event counter packets generation: 0 No POSTCNT underflow packets generated. 1 POSTCNT underflow packets generated, if PCSAMPLENA set to 0. See The POSTCNT timer on page C1-792 for more information. This bit is UNK/SBZP if the NOTRCPKT bit is RAO or the NOCYCCNT bit is RAO.
24	NOPRFCNT	RW	RW	0	Shows whether the implementation supports the profiling counters: 0 Supported. 1 Not supported. For more information see Profiling counter support on page C1-794. This bit is read-only.

Bits	Name	SW	HW	Default or Enum	Description
25	NOCYCCNT	RW	RW	0	Shows whether the implementation supports a cycle counter: 0 Cycle counter supported. 1 Cycle counter not supported. For more information see CYCCNT cycle counter and related timers on page C1-792. This bit is read-only.
26	NOEXTTRIG	RW	RW	0	Shows whether the implementation includes external match signals, CMPMATCH[N]: 0 CMPMATCH[N] supported. 1 CMPMATCH[N] not supported. This bit is read-only.
27	NOTRCPKT	RW	RW	0	Shows whether the implementation supports trace sampling and exception tracing: 0 Trace sampling and exception tracing supported. 1 Trace sampling and exception tracing not supported. If this bit is RAZ, the NOCYCCNT bit must also RAZ. This bit is read-only.
28:31	NUMCOMP	RW	RW	4	Number of comparators implemented. A value of zero indicates no comparator support. These bits are read-only.

4.14.2.2 CM7_DWT_CYCCNT

Description: Cycle Count register

Address: 0xE0001004

Offset: 0x4

Retention: Retained

IsDeepSleep: No

Comment: The CYCCNT register characteristics are:

Purpose: Shows or sets the value of the processor cycle counter, CYCCNT.

Usage constraints: The DWT unit suspends CYCCNT counting when the processor is in Debug state.

Configurations:

Implemented only when CTRL.NOCYCCNT is RAZ, see Control register, CTRL on page C1-797.

When CTRL.NOCYCCNT is RAO no cycle counter is implemented and this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CYCNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CYCNT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CYCNT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CYCNT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CYCNT	RW	RW	0	Incrementing cycle counter value. When enabled, CYCCNT increments on each processor clock cycle. On overflow, CYCCNT wraps to zero.

4.14.2.3 CM7_DWT_CPICNT

Description: CPI Count register

Address: 0xE0001008

Offset: 0x8

Retention: Retained

IsDeepSleep: No

Comment: The CPICNT register characteristics are:

Purpose: Counts additional cycles required to execute multi-cycle instructions and instruction fetch stalls.

Usage constraints: The counter initializes to 0 when software enables its counter overflow event by setting the CTRL.CPIEVTENA bit to 1.

Configurations:

Implemented only when CTRL.NOPRFCNT is RAZ, see Control register, CTRL on page C1-797.

If CTRL.NOPRFCNT is RAO, indicating that the implementation does not include the profiling counters, this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CPICNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CPICNT	RW	RW	0	Base instruction overhead counter. Counts one on each cycle when all of the following are true: - No instruction is executed. - No load-store operation is in progress, see LSU Count register, DWT_LSUCNT on page C1-803. - No exception-entry or exception-exit operation is in progress, see Exception Overhead Count register, DWT_EXCCNT on page C1-802. - Not in a power saving mode, see Sleep Count register, DWT_SLEPCNT on page C1-802. The definition of 'no instruction is executed' is IMPLEMENTATION DEFINED. ARM recommends that this counts each cycle on which no instruction is retired. An event is emitted on counter overflow. Initialized to zero when DWT_CTRL.CPIEVTENA transitions from 0 to 1.

4.14.2.4 CM7_DWT_EXCCNT

Description: Exception Overhead Count register

Address: 0xE000100C

Offset: 0xC

Retention: Retained

IsDeepSleep: No

Comment: The EXCCNT register characteristics are:

Purpose: Counts the total cycles spent in exception processing.

Usage constraints: The counter initializes to 0 when software enables its counter overflow event by setting the CTRL.EXCEVTENA bit to 1.

Configurations

Implemented only when CTRL.NOPRFCNT is RAZ, see Control register, CTRL on page C1-797.

If CTRL.NOPRFCNT is RAO, indicating that the implementation does not include the profiling counters, this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EXCCNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	EXCCNT	RW	RW	0	The exception overhead counter. Counts one on each cycle when all of the following are true: - No instruction is executed, see CPI Count register, DWT_CPICNT on page C1-801. - An exception-entry or exception-exit related operation is in progress. Exception-entry or exception-exit related operations include the stacking of registers on exception entry, unstacking of registers on exception exit, and preemption. An event is emitted on counter overflow. Initialized to zero when DWT_CTRL.EXCEVTENA transitions from 0 to 1.

4.14.2.5 CM7_DWT_SLEPCNT

Description: Sleep Count register

Address: 0xE0001010

Offset: 0x10

Retention: Retained

IsDeepSleep: No

Comment: The SLEPCNT register characteristics are:

Purpose: Counts the total number of cycles that the processor is sleeping.

Usage constraints: The counter initializes to 0 when software enables its counter overflow event by setting the CTRL.SLEEPEVTENA bit to 1.

Configurations:

Implemented only when CTRL.NOPRFCNT is RAZ, see Control register, CTRL on page C1-797.

If CTRL.NOPRFCNT is RAO, indicating that the implementation does not include the profiling counters, this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SLEPCNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SLEPCNT	RW	RW	0	Sleep counter. Counts one on each cycle when all of the following are true: - No instruction is executed, see CPI Count register, DWT_CPICNT on page C1-801. - No load-store operation is in progress, see LSU Count register, DWT_LSUCNT. - No exception-entry or exception-exit operation is in progress, see Exception Overhead Count register, DWT_EXCCNT on page C1-802. - In a power saving mode. Power saving modes include WFI, WFE, and Sleep on exit, see Power management on page B1-616.

4.14.2.6 CM7_DWT_LSUCNT

Description: LSU Count register

Address: 0xE0001014

Offset: 0x14

Retention: Retained

IsDeepSleep: No

Comment: The LSUCNT register characteristics are:

Purpose: Increments on the additional cycles required to execute all load or store instructions

Usage constraints: The counter initializes to 0 when software enables its counter overflow event by setting the CTRL.LSUEVTENA bit to 1.

Configurations:

Implemented only when CTRL.NOPRFCNT is RAZ, see Control register, CTRL on page C1-797.

If CTRL.NOPRFCNT is RAO, indicating that the implementation does not include the profiling counters, this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LSUCNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	LSUCNT	RW	RW	0	Load-store overhead counter. Counts one on each cycle when all of the following are true: - No instruction is executed, see CPI Count register, DWT_CPICNT on page C1-801. - No exception-entry or exception-exit operation is in progress, see Exception Overhead Count register, DWT_EXCCNT on page C1-802. - A load-store operation is in progress.

4.14.2.7 CM7_DWT_FOLDCNT

Description: Folded-instruction Count register

Address: 0xE0001018

Offset: 0x18

Retention: Retained

IsDeepSleep: No

Comment: The FOLDCNT register characteristics are:

Purpose: Increments on each instruction that takes 0 cycles.

Usage constraints:

- The counter initializes to 0 when software enables its counter overflow event by setting the CTRL.FOLDEVTENA bit to 1.

- If an implementation includes profiling counters but does not support instruction folding, this counter can be RAZ/WI.

Configurations:

Implemented only when CTRL.NOPRFCNT is RAZ, see Control register, CTRL on page C1-797.

If CTRL.NOPRFCNT is RAO, indicating that the implementation does not include the profiling counters, this register is UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FOLDCNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	FOLDCNT	RW	RW	0	Folded instruction counter. Counts on each cycle when at least two instructions are executed. The counter is incremented by the number of instructions executed, minus one. At least one instruction is executed is the opposite of No instruction is executed. See CPI Count register, DWT_CPICNT on page C1-801 An event is emitted on counter overflow. Initialized to zero when DWT_CTRL.LSUEVTENA transitions from 0 to 1.

4.14.2.8 CM7_DWT_PCSR

Description: Program Counter Sample Register

Address: 0xE000101C

Offset: 0x1C

Retention: Retained

IsDeepSleep: No

Comment: The PCSR characteristics are:

Purpose: Samples the current value of the program counter.

Usage constraints: There are no usage constraints.

Note: Bit[0] of any sampled value is RAZ and does not reflect instruction set state as it does in a PC sample on the ARMv7-A and ARMv7-R architecture profiles.

Configurations: An optional feature. Register is RAZ/WI if not implemented.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EIASAMPLE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	EIASAMPLE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	EIASAMPLE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	EIASAMPLE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	EIASAMPLE	RW	RW	0	Executed Instruction Address sample value.

4.14.2.9 CM7_DWT_COMP0

Description: Comparator registers

Address: 0xE0001020

Offset: 0x20

Retention: Retained

IsDeepSleep: No

Comment: The COMPn register characteristics are:

Purpose: Provides a reference value for use by comparator n.

Usage constraints: The operation of comparator n depends also on the registers MASKn and FUNCTIONn, see Comparator Mask registers, MASKn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented COMPn registers. Implemented

COMPn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	0	Reference value for comparison.

4.14.2.10 CM7_DWT_MASK0

Description: Comparator Mask registers

Address: 0xE0001024

Offset: 0x24

Retention: Retained

IsDeepSleep: No

Comment: The MASKn register characteristics are:

Purpose: Provides the size of the ignore mask applied to the access address for address range matching by comparator n.

Usage constraints: The operation of comparator n depends also on the registers COMPn and FUNCTIONn, see Comparator registers, COMPn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented MASKn registers. Implemented MASKn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			MASK [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MASK	RW	RW	0	The size of the ignore mask, 0-31 bits, applied to address range matching. The maximum mask size is IMPLEMENTATION DEFINED. A debugger can write 0b11111 to this field and then read the register back to determine the maximum mask size supported.

4.14.2.11 CM7_DWT_FUNCTION0

Description: Comparator Function registers

Address: 0xE0001028

Offset: 0x28

Retention: Retained

IsDeepSleep: No

Comment: The FUNCTIONn register characteristics are:
Purpose: Controls the operation of comparator n.

Usage constraints:

The operation of comparator n depends also on the registers COMPn and MASKn, see Comparator registers, COMPn on page C1-805 and Comparator Mask registers, MASKn on page C1-805.

Reading this register clears some fields to zero. See the register field descriptions for more information, and for the usage constraints of individual fields.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented FUNCTIONn registers. Implemented FUNCTIONn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797. See the register field descriptions for information about the values of the RO bits in the register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CYCMATCH [7:7]	None [6:6]	EMITRANGE [5:5]	None [4:4]	FUNCTION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	DATAVADDR0 [15:12]				DATAVSIZE [11:10]		LNK1ENA [9:9]	DATAVMATCH [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				DATAVADDR1 [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Selects action taken on comparator match: 0000 = Disabled or LinkAddr(), see LinkAddr support on page C1-789. For non-zero values: - If DATAVMATCH is set to 1, see Table C1-16 on page C1-786 - If DATAVMATCH is set to 0 then: - If CYCMATCH is set to 0, see Table C1-14 on page C1-782 - If CYCMATCH is set to 1, see Table C1-15 on page C1-785. This field resets to zero.

Bits	Name	SW	HW	Default or Enum	Description
5	EMITRANGE	RW	RW	0	If the implementation supports trace sampling, enables generation of Data trace address packets, that hold Daddr[15:0]: 0 Data trace address packets disabled. 1 Enable Data trace address packet generation. For more information see Address comparison functions on page C1-781. If DWT_CTRL.NOTRCPKT is RAZ then this bit is UNK/SBZP.
7	CYCMATCH	RW	RW	0	DWT_FUNCTION0 only. If the implementation supports cycle counting, enable cycle count comparison for comparator 0: 0 No comparison is performed. 1 Compare DWT_COMP0 with the cycle counter, DWT_CYCCNT. If DWT_CTRL.NOCYCCNT is RAZ then this bit is UNK/SBZP.
8	DATAVMATCH	RW	RW	0	Enables data value comparison, if supported: 0 Perform address comparison. 1 Perform data value comparison. For comparator 0, when the CYCMATCH is set to 1, DATAVMATCH must be set to 0 for it to perform cycle count comparison. See LNK1ENA, DATAVSIZE, DATAVADDR0 and DATAVADDR1 for related information. If the implementation does not support data value comparison this bit is RAZ/WI.
9	LNK1ENA	RW	RW	0	Indicates whether the implementation supports use of a second linked comparator: 0 Second linked comparator not supported. 1 Second linked comparator supported. When LNK1ENA is RAO, the DATAVADDR1 field specifies the comparator to use as the second linked comparator. This bit is read-only
10:11	DATAVSIZE	RW	RW	0	For data value matching, specifies the size of the required data comparison: 00 Byte. 01 Halfword. 10 Word. The value 0b11 is reserved. Using this value means behavior is UNPREDICTABLE.
12:15	DATAVADDR0	RW	RW	0	When the DATAVMATCH bit is set to 1 this field can hold the comparator number of a comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field if the DATAVMATCH bit is set to 0.
16:19	DATAVADDR1	RW	RW	0	When the DATAVMATCH and LNK1ENA bits are both 1, this field can hold the comparator number of a second comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field unless the LNK1ENA bit is RAO and the DATAVMATCH bit is set to 1. If LNK1ENA is RAZ, this field is RAZ/WI.

Bits	Name	SW	HW	Default or Enum	Description
24	MATCHED	RW	RW	0	Comparator match: 0 No match. 1 Match. A value of 1 indicates that the operation defined by the FUNCTION field occurred since the last read of the register Reading the register clears this bit to 0. This bit is read-only.

4.14.2.12 CM7_DWT_COMP1

Description: Comparator registers

Address: 0xE0001030

Offset: 0x30

Retention: Retained

IsDeepSleep: No

Comment: The COMPn register characteristics are:

Purpose: Provides a reference value for use by comparator n.

Usage constraints: The operation of comparator n depends also on the registers MASKn and FUNCTIONn, see Comparator Mask registers, MASKn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented COMPn registers. Implemented

COMPn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	0	Reference value for comparison.

4.14.2.13 CM7_DWT_MASK1

Description: Comparator Mask registers

Address: 0xE0001034

Offset: 0x34

Retention: Retained

IsDeepSleep: No

Comment: The MASKn register characteristics are:

Purpose: Provides the size of the ignore mask applied to the access address for address range matching by comparator n.

Usage constraints: The operation of comparator n depends also on the registers COMPn and FUNCTIONn, see Comparator registers, COMPn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented MASKn registers. Implemented MASKn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			MASK [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MASK	RW	RW	0	The size of the ignore mask, 0-31 bits, applied to address range matching. The maximum mask size is IMPLEMENTATION DEFINED. A debugger can write 0b11111 to this field and then read the register back to determine the maximum mask size supported.

4.14.2.14 CM7_DWT_FUNCTION1

Description: Comparator Function registers

Address: 0xE0001038

Offset: 0x38

Retention: Retained

IsDeepSleep: No

Comment: The FUNCTIONn register characteristics are:
Purpose: Controls the operation of comparator n.

Usage constraints:

The operation of comparator n depends also on the registers COMPn and MASKn, see Comparator registers, COMPn on page C1-805 and Comparator Mask registers, MASKn on page C1-805.

Reading this register clears some fields to zero. See the register field descriptions for more information, and for the usage constraints of individual fields.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented FUNCTIONn registers. Implemented FUNCTIONn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797. See the register field descriptions for information about the values of the RO bits in the register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CYCMATCH [7:7]	None [6:6]	EMITRANGE [5:5]	None [4:4]	FUNCTION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	DATAVADDR0 [15:12]				DATAVSIZE [11:10]		LNK1ENA [9:9]	DATAVMATCH [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				DATAVADDR1 [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Selects action taken on comparator match: 0000 = Disabled or LinkAddr(), see LinkAddr support on page C1-789. For non-zero values: - If DATAVMATCH is set to 1, see Table C1-16 on page C1-786 - If DATAVMATCH is set to 0 then: - If CYCMATCH is set to 0, see Table C1-14 on page C1-782 - If CYCMATCH is set to 1, see Table C1-15 on page C1-785. This field resets to zero.

Bits	Name	SW	HW	Default or Enum	Description
5	EMITRANGE	RW	RW	0	If the implementation supports trace sampling, enables generation of Data trace address packets, that hold Daddr[15:0]: 0 Data trace address packets disabled. 1 Enable Data trace address packet generation. For more information see Address comparison functions on page C1-781. If DWT_CTRL.NOTRCPKT is RAZ then this bit is UNK/SBZP.
7	CYCMATCH	RW	RW	0	DWT_FUNCTION0 only. If the implementation supports cycle counting, enable cycle count comparison for comparator 0: 0 No comparison is performed. 1 Compare DWT_COMP0 with the cycle counter, DWT_CYCCNT. If DWT_CTRL.NOCYCCNT is RAZ then this bit is UNK/SBZP.
8	DATAVMATCH	RW	RW	0	Enables data value comparison, if supported: 0 Perform address comparison. 1 Perform data value comparison. For comparator 0, when the CYCMATCH is set to 1, DATAVMATCH must be set to 0 for it to perform cycle count comparison. See LNK1ENA, DATAVSIZE, DATAVADDR0 and DATAVADDR1 for related information. If the implementation does not support data value comparison this bit is RAZ/WI.
9	LNK1ENA	RW	RW	0	Indicates whether the implementation supports use of a second linked comparator: 0 Second linked comparator not supported. 1 Second linked comparator supported. When LNK1ENA is RAO, the DATAVADDR1 field specifies the comparator to use as the second linked comparator. This bit is read-only
10:11	DATAVSIZE	RW	RW	0	For data value matching, specifies the size of the required data comparison: 00 Byte. 01 Halfword. 10 Word. The value 0b11 is reserved. Using this value means behavior is UNPREDICTABLE.
12:15	DATAVADDR0	RW	RW	0	When the DATAVMATCH bit is set to 1 this field can hold the comparator number of a comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field if the DATAVMATCH bit is set to 0.
16:19	DATAVADDR1	RW	RW	0	When the DATAVMATCH and LNK1ENA bits are both 1, this field can hold the comparator number of a second comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field unless the LNK1ENA bit is RAO and the DATAVMATCH bit is set to 1. If LNK1ENA is RAZ, this field is RAZ/WI.

Bits	Name	SW	HW	Default or Enum	Description
24	MATCHED	RW	RW	0	Comparator match: 0 No match. 1 Match. A value of 1 indicates that the operation defined by the FUNCTION field occurred since the last read of the register Reading the register clears this bit to 0. This bit is read-only.

4.14.2.15 CM7_DWT_COMP2

Description: Comparator registers

Address: 0xE0001040

Offset: 0x40

Retention: Retained

IsDeepSleep: No

Comment: The COMPn register characteristics are:

Purpose: Provides a reference value for use by comparator n.

Usage constraints: The operation of comparator n depends also on the registers MASKn and FUNCTIONn, see Comparator Mask registers, MASKn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented COMPn registers. Implemented

COMPn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	0	Reference value for comparison.

4.14.2.16 CM7_DWT_MASK2

Description: Comparator Mask registers

Address: 0xE0001044

Offset: 0x44

Retention: Retained

IsDeepSleep: No

Comment: The MASKn register characteristics are:

Purpose: Provides the size of the ignore mask applied to the access address for address range matching by comparator n.

Usage constraints: The operation of comparator n depends also on the registers COMPn and FUNCTIONn, see Comparator registers, COMPn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented MASKn registers. Implemented MASKn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			MASK [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MASK	RW	RW	0	The size of the ignore mask, 0-31 bits, applied to address range matching. The maximum mask size is IMPLEMENTATION DEFINED. A debugger can write 0b11111 to this field and then read the register back to determine the maximum mask size supported.

4.14.2.17 CM7_DWT_FUNCTION2

Description: Comparator Function registers

Address: 0xE0001048

Offset: 0x48

Retention: Retained

IsDeepSleep: No

Comment: The FUNCTIONn register characteristics are:
Purpose: Controls the operation of comparator n.

Usage constraints:

The operation of comparator n depends also on the registers COMPn and MASKn, see Comparator registers, COMPn on page C1-805 and Comparator Mask registers, MASKn on page C1-805.

Reading this register clears some fields to zero. See the register field descriptions for more information, and for the usage constraints of individual fields.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented FUNCTIONn registers. Implemented FUNCTIONn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797. See the register field descriptions for information about the values of the RO bits in the register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CYCMATCH [7:7]	None [6:6]	EMITRANGE [5:5]	None [4:4]	FUNCTION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	DATAVADDR0 [15:12]				DATAVSIZE [11:10]		LNK1ENA [9:9]	DATAVMATCH [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				DATAVADDR1 [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Selects action taken on comparator match: 0000 = Disabled or LinkAddr(), see LinkAddr support on page C1-789. For non-zero values: - If DATAVMATCH is set to 1, see Table C1-16 on page C1-786 - If DATAVMATCH is set to 0 then: - If CYCMATCH is set to 0, see Table C1-14 on page C1-782 - If CYCMATCH is set to 1, see Table C1-15 on page C1-785. This field resets to zero.

Bits	Name	SW	HW	Default or Enum	Description
5	EMITRANGE	RW	RW	0	If the implementation supports trace sampling, enables generation of Data trace address packets, that hold Daddr[15:0]: 0 Data trace address packets disabled. 1 Enable Data trace address packet generation. For more information see Address comparison functions on page C1-781. If DWT_CTRL.NOTRCPKT is RAZ then this bit is UNK/SBZP.
7	CYCMATCH	RW	RW	0	DWT_FUNCTION0 only. If the implementation supports cycle counting, enable cycle count comparison for comparator 0: 0 No comparison is performed. 1 Compare DWT_COMP0 with the cycle counter, DWT_CYCCNT. If DWT_CTRL.NOCYCCNT is RAZ then this bit is UNK/SBZP.
8	DATAVMATCH	RW	RW	0	Enables data value comparison, if supported: 0 Perform address comparison. 1 Perform data value comparison. For comparator 0, when the CYCMATCH is set to 1, DATAVMATCH must be set to 0 for it to perform cycle count comparison. See LNK1ENA, DATAVSIZE, DATAVADDR0 and DATAVADDR1 for related information. If the implementation does not support data value comparison this bit is RAZ/WI.
9	LNK1ENA	RW	RW	0	Indicates whether the implementation supports use of a second linked comparator: 0 Second linked comparator not supported. 1 Second linked comparator supported. When LNK1ENA is RAO, the DATAVADDR1 field specifies the comparator to use as the second linked comparator. This bit is read-only
10:11	DATAVSIZE	RW	RW	0	For data value matching, specifies the size of the required data comparison: 00 Byte. 01 Halfword. 10 Word. The value 0b11 is reserved. Using this value means behavior is UNPREDICTABLE.
12:15	DATAVADDR0	RW	RW	0	When the DATAVMATCH bit is set to 1 this field can hold the comparator number of a comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field if the DATAVMATCH bit is set to 0.
16:19	DATAVADDR1	RW	RW	0	When the DATAVMATCH and LNK1ENA bits are both 1, this field can hold the comparator number of a second comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field unless the LNK1ENA bit is RAO and the DATAVMATCH bit is set to 1. If LNK1ENA is RAZ, this field is RAZ/WI.

Bits	Name	SW	HW	Default or Enum	Description
24	MATCHED	RW	RW	0	Comparator match: 0 No match. 1 Match. A value of 1 indicates that the operation defined by the FUNCTION field occurred since the last read of the register Reading the register clears this bit to 0. This bit is read-only.

4.14.2.18 CM7_DWT_COMP3

Description: Comparator registers

Address: 0xE0001050

Offset: 0x50

Retention: Retained

IsDeepSleep: No

Comment: The COMPn register characteristics are:

Purpose: Provides a reference value for use by comparator n.

Usage constraints: The operation of comparator n depends also on the registers MASKn and FUNCTIONn, see Comparator Mask registers, MASKn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented COMPn registers. Implemented

COMPn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMP [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMP	RW	RW	0	Reference value for comparison.

4.14.2.19 CM7_DWT_MASK3

Description: Comparator Mask registers

Address: 0xE0001054

Offset: 0x54

Retention: Retained

IsDeepSleep: No

Comment: The MASKn register characteristics are:

Purpose: Provides the size of the ignore mask applied to the access address for address range matching by comparator n.

Usage constraints: The operation of comparator n depends also on the registers COMPn and FUNCTIONn, see Comparator registers, COMPn and Comparator Function registers, FUNCTIONn on page C1-806.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented MASKn registers. Implemented MASKn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			MASK [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MASK	RW	RW	0	The size of the ignore mask, 0-31 bits, applied to address range matching. The maximum mask size is IMPLEMENTATION DEFINED. A debugger can write 0b11111 to this field and then read the register back to determine the maximum mask size supported.

4.14.2.20 CM7_DWT_FUNCTION3

Description: Comparator Function registers

Address: 0xE0001058

Offset: 0x58

Retention: Retained

IsDeepSleep: No

Comment: The FUNCTIONn register characteristics are:
Purpose: Controls the operation of comparator n.

Usage constraints:

The operation of comparator n depends also on the registers COMPn and MASKn, see Comparator registers, COMPn on page C1-805 and Comparator Mask registers, MASKn on page C1-805.

Reading this register clears some fields to zero. See the register field descriptions for more information, and for the usage constraints of individual fields.

Configurations:

Implemented only when CTRL.NUMCOMP is nonzero, see Control register, CTRL on page C1-797.

CTRL.NUMCOMP defines the number of implemented FUNCTIONn registers. Implemented FUNCTIONn registers number from 0 to (NUMCOMP-1). Unimplemented registers are UNK/SBZP.

Attributes: See Table C1-21 on page C1-797. See the register field descriptions for information about the values of the RO bits in the register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CYCMATCH [7:7]	None [6:6]	EMITRANGE [5:5]	None [4:4]	FUNCTION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	DATAVADDR0 [15:12]				DATAVSIZE [11:10]		LNK1ENA [9:9]	DATAVMATCH [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				DATAVADDR1 [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							MATCHED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FUNCTION	RW	RW	0	Selects action taken on comparator match: 0000 = Disabled or LinkAddr(), see LinkAddr support on page C1-789. For non-zero values: - If DATAVMATCH is set to 1, see Table C1-16 on page C1-786 - If DATAVMATCH is set to 0 then: - If CYCMATCH is set to 0, see Table C1-14 on page C1-782 - If CYCMATCH is set to 1, see Table C1-15 on page C1-785. This field resets to zero.

Bits	Name	SW	HW	Default or Enum	Description
5	EMITRANGE	RW	RW	0	If the implementation supports trace sampling, enables generation of Data trace address packets, that hold Daddr[15:0]: 0 Data trace address packets disabled. 1 Enable Data trace address packet generation. For more information see Address comparison functions on page C1-781. If DWT_CTRL.NOTRCPKT is RAZ then this bit is UNK/SBZP.
7	CYCMATCH	RW	RW	0	DWT_FUNCTION0 only. If the implementation supports cycle counting, enable cycle count comparison for comparator 0: 0 No comparison is performed. 1 Compare DWT_COMP0 with the cycle counter, DWT_CYCCNT. If DWT_CTRL.NOCYCCNT is RAZ then this bit is UNK/SBZP.
8	DATAVMATCH	RW	RW	0	Enables data value comparison, if supported: 0 Perform address comparison. 1 Perform data value comparison. For comparator 0, when the CYCMATCH is set to 1, DATAVMATCH must be set to 0 for it to perform cycle count comparison. See LNK1ENA, DATAVSIZE, DATAVADDR0 and DATAVADDR1 for related information. If the implementation does not support data value comparison this bit is RAZ/WI.
9	LNK1ENA	RW	RW	0	Indicates whether the implementation supports use of a second linked comparator: 0 Second linked comparator not supported. 1 Second linked comparator supported. When LNK1ENA is RAO, the DATAVADDR1 field specifies the comparator to use as the second linked comparator. This bit is read-only
10:11	DATAVSIZE	RW	RW	0	For data value matching, specifies the size of the required data comparison: 00 Byte. 01 Halfword. 10 Word. The value 0b11 is reserved. Using this value means behavior is UNPREDICTABLE.
12:15	DATAVADDR0	RW	RW	0	When the DATAVMATCH bit is set to 1 this field can hold the comparator number of a comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field if the DATAVMATCH bit is set to 0.
16:19	DATAVADDR1	RW	RW	0	When the DATAVMATCH and LNK1ENA bits are both 1, this field can hold the comparator number of a second comparator to use for linked address comparison. For more information see LinkAddr support on page C1-789. The DWT unit ignores the value of this field unless the LNK1ENA bit is RAO and the DATAVMATCH bit is set to 1. If LNK1ENA is RAZ, this field is RAZ/WI.

Bits	Name	SW	HW	Default or Enum	Description
24	MATCHED	RW	RW	0	Comparator match: 0 No match. 1 Match. A value of 1 indicates that the operation defined by the FUNCTION field occurred since the last read of the register Reading the register clears this bit to 0. This bit is read-only.

4.14.2.21 CM7_DWT_LAR

Description: Lock Access Register
Address: 0xE0001FB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	N/A

4.14.2.22 CM7_DWT_LSR

Description: Lock Status Register
Address: 0xE0001FB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.2.23 CM7_DWT_PID4

Description: Peripheral Identification Register 4.
Address: 0xE0001FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.2.24 CM7_DWT_PID5

Description: Peripheral Identification Register 5.
Address: 0xE0001FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.2.25 CM7_DWT_PID6

Description: Peripheral Identification Register 6.
Address: 0xE0001FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.2.26 CM7_DWT_PID7

Description: Peripheral Identification Register 7.
Address: 0xE0001FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.2.27 CM7_DWT_PID0

Description: Peripheral Identification Register 0.
Address: 0xE0001FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	2	N/A

4.14.2.28 CM7_DWT_PID1

Description: Peripheral Identification Register 1.
Address: 0xE0001FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	N/A

4.14.2.29 CM7_DWT_PID2

Description: Peripheral Identification Register 2.
Address: 0xE0001FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	N/A

4.14.2.30 CM7_DWT_PID3

Description: Peripheral Identification Register 3.
Address: 0xE0001FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision

4.14.2.31 CM7_DWT_CID0

Description: Component Identification Register 0.
Address: 0xE0001FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.2.32 CM7_DWT_CID1

Description: Component Identification Register 1.
Address: 0xE0001FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	N/A

4.14.2.33 CM7_DWT_CID2

Description: Component Identification Register 2.
Address: 0xE0001FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.2.34 CM7_DWT_CID3

Description: Component Identification Register 3.
Address: 0xE0001FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.3 FPB

4.14.3.1 CM7_FPB_CTRL

Description: FlashPatch Control Register

Address: 0xE0002000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: The FP_CTRL Register characteristics are:

Purpose: Provides FPB implementation information, and the global enable for the FPB unit.

Usage constraints: There are no usage constraints.

Configurations: Always implemented.

Attributes: See Table C1-23.

Default: 0x260

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NUM_CODE_LO [7:4]				None [3:2]		KEY [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	NUM_CODE_HI [14:12]			NUM_LIT [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REV [31:28]				None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	0	Enable bit for the FPB: 0 Flash Patch Breakpoint disabled. 1 Flash Patch Breakpoint enabled. A Power-on reset clears this bit to 0.
1	KEY	RW	RW	0	On any write to FP_CTRL, this bit must be 1. A write to the register with this bit set to zero is ignored. The Flash Patch Breakpoint unit ignores the write unless this bit is 1. This bit is RAZ.
4:7	NUM_CODE_LO	RW	RW	6	The least significant bits, being bits[3:0], of NUM_CODE, the number of instruction address comparators. If NUM_CODE[6:0] is zero, the implementation does not support any instruction address comparators. These bits are read only.
8:11	NUM_LIT	RW	RW	2	The number of literal address comparators supported, starting from NUM_CODE upwards. UNK/SBZP if Flash Patch is not implemented. Flash Patch is not implemented if FP_REMAP[29] is 0. If this field is zero, the implementation does not support literal comparators. These bits are read-only.
12:14	NUM_CODE_HI	RW	RW	0	The most significant bits, being bits[6:4], of NUM_CODE, the number of instruction address comparators, see bits[7:4]. These bits are read only.

Bits	Name	SW	HW	Default or Enum	Description
28:31	REV	RW	RW	0	Flash Patch Breakpoint architecture revision: 0000 Flash Patch Breakpoint version 1. 0001 Flash Patch Breakpoint version 2. Supports breakpoints on any location in the 4GB address range.

4.14.3.2 CM7_FPB_REMAP

Description: FlashPatch Remap register

Address: 0xE0002004

Offset: 0x4

Retention: Retained

IsDeepSleep: No

Comment: The FP_REMAP register characteristics are:

Purpose: Indicates whether the implementation supports flash patch remap, and if it does, holds the SRAM address for remap.

Usage constraints: There are no usage constraints.

Configurations: Not Implemented. RAZ/WI for CM7.

Attributes: See Table C1-23 on page C1-816.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name						None [4:0]		

Bits	15	14	13	12	11	10	9	8
Name	REMAP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMAP [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RMPSP [31:30]		None [29:29]	REMAP [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
5:28	REMAP	RW	RW	0	If the FPB supports flash patch remap, this field: - Holds bits[28:5] of the base address in SRAM to which the FPB remaps the address. - Has an UNKNOWN value on reset. If the FPB only supports breakpoint functionality this field is UNK/SBZP.
30:31	RMPSP	RW	RW	0	Indicates whether the FPB unit supports flash patch remap: 0 Remapping not supported. The FPB only supports breakpoint functionality. 1 Hard-wired remap to SRAM region. These bits are read only.

4.14.3.3 CM7_FP_COMP

Description: FlashPatch Comparator register

Address: 0xE0002008

Offset: 0x8

Retention: Retained

IsDeepSleep: No

Comment: The FP_COMPn register characteristics are:

Purpose:

Holds an address for comparison with addresses in the Code memory region, see The system address map on page B3-648. The effect of a match depends on whether the comparator is an instruction address comparator or a literal address comparator:

Instruction address comparators

Either:

- Defines an instruction address to remap to an address based on the address specified in the FP_REMAP register.

- Defines a breakpoint address.

Literal address comparators

Defines a literal address to remap to an address based on the address specified in the FP_REMAP register.

The FP_CTRL register determines which comparators are instruction address comparators and which are literal address comparators. The version of the FPB unit determines the bit assignment for the FP_COMP register. The FP_CTRL.REV field determines which version of the FPB unit is attached. See FlashPatch Control Register, FP_CTRL on page C1-816.

The FP_REMAP.RMPSP field determines if the FPB unit supports Flash Patch. For more information about address remapping see FlashPatch Remap register, FP_REMAP on page C1-818.

If the FPB unit is configured for remap then FP_COMPn defines a 29-bit word-aligned address.

If the FPB unit is configured for breakpoints, version 1 defines a 29-bit word-aligned address and the breakpoint can be set on either or both half-words at this address. For version 2 FPB units configured for breakpoints, FP_COMPn defines a 32-bit half-word aligned address.

Usage constraints: To enable a comparator, both the FP_CTRL.ENABLE bit and the required FP_COMPn.ENABLE bit must be set to 1.

Configuration: Always implemented. see FlashPatch Control Register, FP_CTRL on page C1-816 for information about the number of implemented FlashPatch comparator registers.

Attributes: See Table C1-23 on page C1-816.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	See ARM documentation for details.

4.14.3.4 CM7_FPB_LAR

Description: Lock Access Register
Address: 0xE0002FB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	N/A

4.14.3.5 CM7_FPB_LSR

Description: Lock Status Register
Address: 0xE0002FB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.3.6 CM7_FPB_PID4

Description: Peripheral Identification Register 4.
Address: 0xE0002FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.3.7 CM7_FPB_PID5

Description: Peripheral Identification Register 5.
Address: 0xE0002FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.3.8 CM7_FPB_PID6

Description: Peripheral Identification Register 6.
Address: 0xE0002FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.3.9 CM7_FPB_PID7

Description: Peripheral Identification Register 7.
Address: 0xE0002FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.3.10 CM7_FPB_PID0

Description: Peripheral Identification Register 0.
Address: 0xE0002FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	14	N/A

4.14.3.11 CM7_FPB_PID1

Description: Peripheral Identification Register 1.
Address: 0xE0002FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	N/A

4.14.3.12 CM7_FPB_PID2

Description: Peripheral Identification Register 2.
Address: 0xE0002FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	N/A

4.14.3.13 CM7_FPB_PID3

Description: Peripheral Identification Register 3.
Address: 0xE0002FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision

4.14.3.14 CM7_FPB_CID0

Description: Component Identification Register 0.
Address: 0xE0002FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.3.15 CM7_FPB_CID1

Description: Component Identification Register 1.
Address: 0xE0002FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	N/A

4.14.3.16 CM7_FPB_CID2

Description: Component Identification Register 2.
Address: 0xE0002FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.3.17 CM7_FPB_CID3

Description: Component Identification Register 3.
Address: 0xE0002FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.4 SCS

4.14.4.1 CM7_SCS_ACTLR

Description: Auxiliary Control Register
Address: 0xE000E008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer the following ARM documents for details about CPU register descriptions: ARMV7M : http://infocenter.arm.com/help/index.jsp?topic=/com.arm.doc.ddi0403e.d/index.html CM7 TRM: http://infocenter.arm.com/help/index.jsp?topic=/com.arm.doc.ddi0489f/index.html

4.14.4.2 CM7_SCS_SYST_CSR

Description: SysTick Control and Status Register
Address: 0xE000E010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.3 CM7_SCS_SYST_RVR

Description: SysTick Reload Value Register
Address: 0xE000E014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.4 CM7_SCS_SYST_CVR

Description: SysTick Current Value Register
Address: 0xE000E018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.5 CM7_SCS_SYST_CALIB

Description: SysTick Calibration value Register
Address: 0xE000E01C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.6 CM7_SCS_NVIC_ISER

Description: Interrupt Set-Enable Registers
Address: 0xE000E100
Offset: 0x100
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.7 CM7_SCS_NVIC_ICER

Description: Interrupt Clear-Enable Registers
Address: 0xE000E180
Offset: 0x180
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.8 CM7_SCS_NVIC_ISPR

Description: Interrupt Set-Pending Registers
Address: 0xE000E200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.9 CM7_SCS_NVIC_ICPR

Description: Interrupt Clear-Pending Registers
Address: 0xE000E280
Offset: 0x280
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.10 CM7_SCS_NVIC_IABR

Description: Interrupt Active Bit Registers
Address: 0xE000E300
Offset: 0x300
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.11 CM7_SCS_NVIC_IPR

Description: Interrupt Priority Registers
Address: 0xE000E400
Offset: 0x400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.12 CM7_SCS_CPUID

Description: CPUID Base Register
Address: 0xE000ED00
Offset: 0xD00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.13 CM7_SCS_ICSR

Description: Interrupt Control and State Register
Address: 0xE000ED04
Offset: 0xD04
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.14 CM7_SCS_VTOR

Description: Vector Table Offset Register
Address: 0xE000ED08
Offset: 0xD08
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.15 CM7_SCS_AIRCR

Description: Application Interrupt and Reset Control Register
Address: 0xE000ED0C
Offset: 0xD0C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.16 CM7_SCS_SCR

Description: System Control Register
Address: 0xE000ED10
Offset: 0xD10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.17 CM7_SCS_CCR

Description: Configuration and Control Register
Address: 0xE000ED14
Offset: 0xD14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.18 CM7_SCS_SHPR1

Description: System Handler Priority Register 1
Address: 0xE000ED18
Offset: 0xD18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.19 CM7_SCS_SHPR2

Description: System Handler Priority Register 2
Address: 0xE000ED1C
Offset: 0xD1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.20 CM7_SCS_SHPR3

Description: System Handler Priority Register 3
Address: 0xE000ED20
Offset: 0xD20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.21 CM7_SCS_SHCSR

Description: System Handler Control and State Register
Address: 0xE000ED24
Offset: 0xD24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.22 CM7_SCS_CFSR

Description: Configurable Fault Status Register
Address: 0xE000ED28
Offset: 0xD28
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.23 CM7_SCS_HFSR

Description: HardFault Status Register
Address: 0xE000ED2C
Offset: 0xD2C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.24 CM7_SCS_DFSR

Description: Debug Fault Status Register
Address: 0xE000ED30
Offset: 0xD30
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.25 CM7_SCS_MM FAR

Description: MemManage Fault Address Register
Address: 0xE000ED34
Offset: 0xD34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.26 CM7_SCS_BFAR

Description: BusFault Address Register
Address: 0xE000ED38
Offset: 0xD38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.27 CM7_SCS_ID_PFR0

Description: Processor Feature Register 0
Address: 0xE000ED40
Offset: 0xD40
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x30

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	48	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.28 CM7_SCS_ID_PFR1

Description: Processor Feature Register 1
Address: 0xE000ED44
Offset: 0xD44
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x200

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	512	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.29 CM7_SCS_ID_DFR0

Description: Debug Feature Register 0
Address: 0xE000ED48
Offset: 0xD48
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x100000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1048576	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.30 CM7_SCS_ID_AFR0

Description: Auxiliary Feature Register 0
Address: 0xE000ED4C
Offset: 0xD4C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.31 CM7_SCS_ID_MMFR0

Description: Memory Model Feature Register 0
Address: 0xE000ED50
Offset: 0xD50
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x100030

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1048624	Reset value depends on ITCMSIZE and DTCMSIZE. Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.32 CM7_SCS_ID_MMFR1

Description: Memory Model Feature Register 1
Address: 0xE000ED54
Offset: 0xD54
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.33 CM7_SCS_ID_MMFR2

Description: Memory Model Feature Register 2
Address: 0xE000ED58
Offset: 0xD58
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16777216	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.34 CM7_SCS_ID_MMFR3

Description: Memory Model Feature Register 3
Address: 0xE000ED5C
Offset: 0xD5C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.35 CM7_SCS_ID_ISAR0

Description: Instruction Set Attributes Register 0
Address: 0xE000ED60
Offset: 0xD60
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1101110

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	17830160	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.36 CM7_SCS_ID_ISAR1

Description: Instruction Set Attributes Register 1
Address: 0xE000ED64
Offset: 0xD64
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2112000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	34676736	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.37 CM7_SCS_ID_ISAR2

Description: Instruction Set Attributes Register 2
Address: 0xE000ED68
Offset: 0xD68
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x20232231

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	539173425	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.38 CM7_SCS_ID_ISAR3

Description: Instruction Set Attributes Register 3
Address: 0xE000ED6C
Offset: 0xD6C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1111131

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	17895729	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.39 CM7_SCS_ID_ISAR4

Description: Instruction Set Attributes Register 4
Address: 0xE000ED70
Offset: 0xD70
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1310132

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	19988786	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.40 CM7_SCS_CLIDR

Description: Cache Level ID Register
Address: 0xE000ED78
Offset: 0xD78
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x9000003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	150994947	Value depends on cache implementation. Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.41 CM7_SCS_CTR

Description: Cache Type Register
Address: 0xE000ED7C
Offset: 0xD7C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x8303C003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	2198061059	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.42 CM7_SCS_CC SIDR

Description: Cache Size ID Register
Address: 0xE000ED80
Offset: 0xD80
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.43 CM7_SCS_CSSELR

Description: Cache Size Selection Register
Address: 0xE000ED84
Offset: 0xD84
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.44 CM7_SCS_CPACR

Description: Coprocessor Access Control Register
Address: 0xE000ED88
Offset: 0xD88
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.45 CM7_SCS_MPU_TYPE

Description: MPU Type Register
Address: 0xE000ED90
Offset: 0xD90
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.46 CM7_SCS_MPU_CTRL

Description: MPU Control Register
Address: 0xE000ED94
Offset: 0xD94
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.47 CM7_SCS_MPU_RNR

Description: MPU Region Number Register
Address: 0xE000ED98
Offset: 0xD98
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.48 CM7_SCS_MPU_RBAR

Description: MPU Region Base Address Register
Address: 0xE000ED9C
Offset: 0xD9C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.49 CM7_SCS_MPU_RASR

Description: MPU Region Attribute and Size Register
Address: 0xE000EDA0
Offset: 0xDA0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.50 CM7_SCS_MPU_RBAR_A1

Description: MPU alias registers
Address: 0xE000EDA4
Offset: 0xDA4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.51 CM7_SCS_MPU_RASR_A1

Description: MPU alias registers
Address: 0xE000EDA8
Offset: 0xDA8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.52 CM7_SCS_MPU_RBAR_A2

Description: MPU alias registers
Address: 0xE000EDAC
Offset: 0xDAC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.53 CM7_SCS_MPU_RASR_A2

Description: MPU alias registers
Address: 0xE000EDB0
Offset: 0xDB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.54 CM7_SCS_MPU_RBAR_A3

Description: MPU alias registers
Address: 0xE000EDB4
Offset: 0xDB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.55 CM7_SCS_MPU_RASR_A3

Description: MPU alias registers
Address: 0xE000EDB8
Offset: 0xDB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.56 CM7_SCS_DHCSR

Description: Debug Halting Control and Status Register
Address: 0xE000EDF0
Offset: 0xDF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.57 CM7_SCS_DCRSR

Description: Debug Core Register Selector Register
Address: 0xE000EDF4
Offset: 0xDF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.58 CM7_SCS_DCRDR

Description: Debug Core Register Data Register
Address: 0xE000EDF8
Offset: 0xDF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.59 CM7_SCS_DEMCR

Description: Debug Exception and Monitor Control Register
Address: 0xE000EDFC
Offset: 0xDFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.60 CM7_SCS_STIR

Description: Software Triggered Interrupt Register
Address: 0xE000EF00
Offset: 0xF00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.61 CM7_SCS_FPCCR

Description: FP Context Control Register
Address: 0xE000EF34
Offset: 0xF34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.62 CM7_SCS_FPCAR

Description: FP Context Control Register
Address: 0xE000EF38
Offset: 0xF38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.63 CM7_SCS_FPDSCR

Description: FP Context Control Register
Address: 0xE000EF3C
Offset: 0xF3C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.64 CM7_SCS_MVFR0

Description: Media and VFP Feature Register 0
Address: 0xE000EF40
Offset: 0xF40
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10110221

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	269550113	0x10110221 for Double Precision FPU; 0x10110021 for Single Precision FPU.

4.14.4.65 CM7_SCS_MVFR1

Description: Media and VFP Feature Register 1
Address: 0xE000EF44
Offset: 0xF44
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x12000011

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	301989905	0x12000011 for Double Precision FPU; 0x11000011 for Single Precision FPU.

4.14.4.66 CM7_SCS_MVFR2

Description: Media and VFP Feature Register 2
Address: 0xE000EF48
Offset: 0xF48
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	64	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.67 CM7_SCS_ICIALLU

Description: Instruction cache invalidate all to Point of Unification (PoU)
Address: 0xE000EF50
Offset: 0xF50
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.68 CM7_SCS_ICIMVAU

Description: Instruction cache invalidate by address to PoU
Address: 0xE000EF58
Offset: 0xF58
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.69 CM7_SCS_DCIMVAC

Description: Data cache invalidate by address to Point of Coherency (PoC)
Address: 0xE000EF5C
Offset: 0xF5C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.70 CM7_SCS_DCISW

Description: Data cache invalidate by set/way
Address: 0xE000EF60
Offset: 0xF60
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.71 CM7_SCS_DCCMVAU

Description: Data cache by address to PoU
Address: 0xE000EF64
Offset: 0xF64
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.72 CM7_SCS_DCCMVAC

Description: Data cache clean by address to PoU
Address: 0xE000EF68
Offset: 0xF68
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.73 CM7_SCS_DCCSW

Description: Data cache clean by set/way
Address: 0xE000EF6C
Offset: 0xF6C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.74 CM7_SCS_DCCIMVAC

Description: Data cache clean and invalidate by address to PoC
Address: 0xE000EF70
Offset: 0xF70
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.75 CM7_SCS_DCCISW

Description: Data cache clean and invalidate by set/way
Address: 0xE000EF74
Offset: 0xF74
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	Undefined	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.76 CM7_SCS_CM7_ITCMCR

Description: Instruction Tightly Coupled Memory Control Register
Address: 0xE000EF90
Offset: 0xF90
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.77 CM7_SCS_CM7_DTCMCR

Description: Data Tightly Coupled Memory Control Register
Address: 0xE000EF94
Offset: 0xF94
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.78 CM7_SCS_CM7_AHBPCR

Description: AHBP Control Register
Address: 0xE000EF98
Offset: 0xF98
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.79 CM7_SCS_CM7_CACR

Description: L1 Cache Control Register
Address: 0xE000EF9C
Offset: 0xF9C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.80 CM7_SCS_CM7_AHBSCR

Description: AHB Slave Control Register
Address: 0xE000EFA0
Offset: 0xFA0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.81 CM7_SCS_CM7_ABFSR

Description: Auxiliary Bus Fault Status Register
Address: 0xE000EFA8
Offset: 0xFA8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.82 CM7_SCS_IEBR0

Description: Instruction Error bank Register 0
Address: 0xE000EFB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.83 CM7_SCS_IEBR1

Description: Instruction Error bank Register 1
Address: 0xE000EFB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.84 CM7_SCS_DEBR0

Description: Data Error Bank Register 0
Address: 0xE000EFB8
Offset: 0xFB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.85 CM7_SCS_DEBR1

Description: Data Error Bank Register 1
Address: 0xE000EFBC
Offset: 0xFBC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARMv7M architecture spec and CM7 TRM for description. See links in CM7_SCS.ACTLR description.

4.14.4.86 CM7_SCS_PID4

Description: Peripheral Identification Register 4
Address: 0xE000EFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.4.87 CM7_SCS_PID5

Description: Peripheral Identification Register 5
Address: 0xE000EFD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.4.88 CM7_SCS_PID6

Description: Peripheral Identification Register 6
Address: 0xE000EFD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.4.89 CM7_SCS_PID7

Description: Peripheral Identification Register 7
Address: 0xE000EFDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.4.90 CM7_SCS_PID0

Description: Peripheral Identification Register 0
Address: 0xE000EFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	12	Table 9-5 of CM7 TRM. It states 0x0000000C is identification value for implementations without FPU. What is it with FPU?

4.14.4.91 CM7_SCS_PID1

Description: Peripheral Identification Register 1
Address: 0xE000EFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	176	N/A

4.14.4.92 CM7_SCS_PID2

Description: Peripheral Identification Register 2
Address: 0xE000EFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	N/A

4.14.4.93 CM7_SCS_PID3

Description: Peripheral Identification Register 3
Address: 0xE000EFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	N/A

4.14.4.94 CM7_SCS_CID0

Description: Component Identification Register 0
Address: 0xE000EFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.4.95 CM7_SCS_CID1

Description: Component Identification Register 1
Address: 0xE000EFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xE0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	224	N/A

4.14.4.96 CM7_SCS_CID2

Description: Component Identification Register 2
Address: 0xE000EFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.4.97 CM7_SCS_CID3

Description: Component Identification Register 3
Address: 0xE000E0FC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.5 ETM

4.14.5.1 CM7_ETM_TRCPRGCTLR

Description: Programming Control Register
Address: 0xE0041004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer the following ARM CM7 ETM TRM for register description: http://infocenter.arm.com/help/index.jsp?topic=/com.arm.doc.ddi0494d/index.html

4.14.5.2 CM7_ETM_TRCSTATR

Description: Status Register
Address: 0xE004100C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.5.3 CM7_ETM_TRCCONFIGR

Description: Trace Configuration Register
Address: 0xE0041010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.4 CM7_ETM_TRCEVENTCTL0R

Description: Event Control 0 Register
Address: 0xE0041020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.5 CM7_ETM_TRCEVENTCTL1R

Description: Event Control 1 Register
Address: 0xE0041024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.6 CM7_ETM_TRCSTALLCTL

Description: Stall Control Register
Address: 0xE004102C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.7 CM7_ETM_TRCTSCTLR

Description: Global Timestamp Control Register
Address: 0xE0041030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.8 CM7_ETM_TRCSYNCP

Description: Synchronization Period Register
Address: 0xE0041034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xA

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	10	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.9 CM7_ETM_TRCCCCTL

Description: Cycle Count Control Register
Address: 0xE0041038
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.10 CM7_ETM_TRCTRACEIDR

Description: Trace ID Register
Address: 0xE0041040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.11 CM7_ETM_TRCVICTLR

Description: ViewInst Main Control Register
Address: 0xE0041080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.12 CM7_ETM_TRCVIPCSSCTLR

Description: ViewInst Start-Stop Processor Comparator Control Register
Address: 0xE004108C
Offset: 0x8C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.13 CM7_ETM_TRCCNTRLDVR

Description: Counter Reload Value Registers
Address: 0xE0041140
Offset: 0x140
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.14 CM7_ETM_TRCIDR8

Description: ID Register 8
Address: 0xE0041180
Offset: 0x180
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.15 CM7_ETM_TRCIDR9

Description: ID Register 9
Address: 0xE0041184
Offset: 0x184
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.16 CM7_ETM_TRCIDR10

Description: ID Register 10
Address: 0xE0041188
Offset: 0x188
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.17 CM7_ETM_TRCIDR11

Description: ID Register 11
Address: 0xE004118C
Offset: 0x18C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.18 CM7_ETM_TRCIDR12

Description: ID Register 12
Address: 0xE0041190
Offset: 0x190
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.19 CM7_ETM_TRCIDR13

Description: ID Register 13
Address: 0xE0041194
Offset: 0x194
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.20 CM7_ETM_TRCIMPSPCO

Description: Implementation Specific Register 0
Address: 0xE00411C0
Offset: 0x1C0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.21 CM7_ETM_TRCIDR0

Description: ID Register 0
Address: 0xE00411E0
Offset: 0x1E0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC000EE1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	201330401	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.22 CM7_ETM_TRCIDR1

Description: ID Register 1
Address: 0xE00411E4
Offset: 0x1E4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4100F401

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1090581505	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.23 CM7_ETM_TRCIDR2

Description: ID Register 2
Address: 0xE00411E8
Offset: 0x1E8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.24 CM7_ETM_TRCIDR3

Description: ID Register 3
Address: 0xE00411EC
Offset: 0x1EC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x37090004

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	923336708	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.25 CM7_ETM_TRCIDR4

Description: ID Register 4
Address: 0xE00411F0
Offset: 0x1F0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x114000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1130496	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.26 CM7_ETM_TRCIDR5

Description: ID Register 5
Address: 0xE00411F4
Offset: 0x1F4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90C70002

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	242896077 0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.27 CM7_ETM_TRCSRCLR2

Description: Resource Selection Register 2
Address: 0xE0041208
Offset: 0x208
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.28 CM7_ETM_TRCSRCLR3

Description: Resource Selection Register 3
Address: 0xE004120C
Offset: 0x20C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.29 CM7_ETM_TRCSSCCR0

Description: Single-shot Comparator Control Register0
Address: 0xE0041280
Offset: 0x280
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.30 CM7_ETM_TRCSSCSR0

Description: Single-shot Comparator Status Register 0
Address: 0xE00412A0
Offset: 0x2A0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.31 CM7_ETM_TRCSSPCICR0

Description: Single-shot Comparator Status Register 0
Address: 0xE00412C0
Offset: 0x2C0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.32 CM7_ETM_TRCOSLSR

Description: OS Lock Status Register
Address: 0xE0041304
Offset: 0x304
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.33 CM7_ETM_TRCPDCR

Description: Power Down Control Register
Address: 0xE0041310
Offset: 0x310
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.34 CM7_ETM_TRCPDSR

Description: Power Down Status Register
Address: 0xE0041314
Offset: 0x314
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	3	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.35 CM7_ETM_TRCITMISCOUTR

Description: Integration Miscellaneous Outputs Register
Address: 0xE0041EDC
Offset: 0xEDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.36 CM7_ETM_TRCITMISCINR

Description: Integration Miscellaneous Inputs Register
Address: 0xE0041EE0
Offset: 0xEE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.37 CM7_ETM_TRCITATBIDR

Description: Integration ATB Identification Register
Address: 0xE0041EE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.38 CM7_ETM_TRCITDDATAR

Description: Integration Data ATB Data Register
Address: 0xE0041EE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.39 CM7_ETM_TRCIDATAR

Description: Integration Instruction ATB Data Register
Address: 0xE0041EEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.40 CM7_ETM_TRCITDATBINR

Description: Integration Data ATB In Register
Address: 0xE0041EF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.41 CM7_ETM_TRCITIATBINR

Description: Integration Instruction ATB In Register
Address: 0xE0041EF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.42 CM7_ETM_TRCITDATBOUTR

Description: Integration Data ATB Out Register
Address: 0xE0041EF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.43 CM7_ETM_TRCITIATBOUTR

Description: Integration Instruction ATB Out Register
Address: 0xE0041EFC
Offset: 0xEFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.44 CM7_ETM_TRCITCTRL

Description: Integration Mode Control Register
Address: 0xE0041F00
Offset: 0xF00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.45 CM7_ETM_TRCCLAIMSET

Description: Claim Tag Set Register
Address: 0xE0041FA0
Offset: 0xFA0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	4	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.46 CM7_ETM_TRCCLAIMCLR

Description: Claim Tag Clear Register
Address: 0xE0041FA4
Offset: 0xFA4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.47 CM7_ETM_TRCLAR

Description: Software Lock Access Register
Address: 0xE0041FB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	W	W	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.48 CM7_ETM_TRCLSR

Description: Software Lock Status Register
Address: 0xE0041FB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.49 CM7_ETM_TRCAUTHSTATUS

Description: Authentication Status Register
Address: 0xE0041FB8
Offset: 0xFB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.50 CM7_ETM_TRCDEVARCH

Description: Device Architecture Register
Address: 0xE0041FBC
Offset: 0xFBC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x47704A13

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	119854133 1	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.51 CM7_ETM_TRCDEVID

Description: Device ID Register
Address: 0xE0041FC8
Offset: 0xFC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.52 CM7_ETM_TRCDEVTYPE

Description: CoreSight Device Type Register
Address: 0xE0041FCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x13

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	19	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.53 CM7_ETM_PID4

Description: Peripheral Identification Register 4.
Address: 0xE0041FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.54 CM7_ETM_PID5

Description: Peripheral Identification Register 5.
Address: 0xE0041FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.55 CM7_ETM_PID6

Description: Peripheral Identification Register 6.
Address: 0xE0041FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.56 CM7_ETM_PID7

Description: Peripheral Identification Register 7.
Address: 0xE0041FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.57 CM7_ETM_PID0

Description: Peripheral Identification Register 0.
Address: 0xE0041FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x75

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	117	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.58 CM7_ETM_PID1

Description: Peripheral Identification Register 1.
Address: 0xE0041FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.59 CM7_ETM_PID2

Description: Peripheral Identification Register 2.
Address: 0xE0041FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	27	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.60 CM7_ETM_PID3

Description: Peripheral Identification Register 3.
Address: 0xE0041FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.61 CM7_ETM_CID0

Description: Component Identification Register 0.
Address: 0xE0041FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.62 CM7_ETM_CID1

Description: Component Identification Register 1.
Address: 0xE0041FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.63 CM7_ETM_CID2

Description: Component Identification Register 2.
Address: 0xE0041FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.5.64 CM7_ETM_CID3

Description: Component Identification Register 3.
Address: 0xE0041FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Refer ARM documentation. See links in CM7_ETM_TRCPRGCTLR.

4.14.6 CM7CTI

4.14.6.1 CM7_CM7CTI_CTICONTROL

Description: CTI Control Register
Address: 0xE0042000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: The CTI Control Register enables the CTI.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							GLBEN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GLBEN	RW	RW	0	Enables or disables the ECT: 0 = disabled (reset) 1 = enabled. When disabled, all cross triggering mapping logic functionality is disabled for this processor.

4.14.6.2 CM7_CM7CTI_CTIINTACK

Description: CTI Interrupt Acknowledge Register
Address: 0xE0042010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: The CTI Interrupt Acknowledge Register is write-only. Any bits written as a 1 cause the CTITRIGOUT output signal to be acknowledged. The acknowledgement is cleared when MAPTRIGOUT is deactivated. This register is used when the CTITRIGOUT is used as a sticky output, that is, no hardware acknowledge is supplied, and a software acknowledge is required.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INTACK [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INTACK	W	W	0	Acknowledges the corresponding CTITRIGOUT output: 1 = CTITRIGOUT is acknowledged and is cleared when MAPTRIGOUT is LOW. 0 = no effect. There is one bit of the register for each CTITRIGOUT output.

4.14.6.3 CM7_CM7CTI_CTIAPPSET

Description: CTI Application Trigger Set Register
Address: 0xE0042014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Set Register is read/write. A write to this register causes a channel event to be raised, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPSET [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPSET	RW	RW	0	Setting a bit HIGH generates a channel event for the selected channel. Read: 0 = application trigger inactive (reset) 1 = application trigger active. Write: 0 = no effect 1 = generate channel event. There is one bit of the register for each channel.

4.14.6.4 CM7_CM7CTI_CTIAPPCLEAR

Description: CTI Application Trigger Clear Register
Address: 0xE0042018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Clear Register is write-only. A write to this register causes a channel event to be cleared, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPCLEAR [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPCLEAR	W	W	0	Clears corresponding bits in the CTIAPPSET register. 1 = application trigger disabled in the CTIAPPSET register 0 = no effect. There is one bit of the register for each channel.

4.14.6.5 CM7_CM7CTI_CTIAPPPULSE

Description: CTI Application Pulse Register

Address: 0xE004201C

Offset: 0x1C

Retention: Retained

IsDeepSleep: No

Comment: The CTI Application Pulse Register is write-only. A write to this register causes a channel event pulse, one CTICLK period, to be generated, corresponding to the bit written to. The pulse external to the ECT can be extended to multi-cycle by the handshaking interface circuits. This register clears itself immediately, so it can be repeatedly written to without software having to clear it.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPULSE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPULSE	W	W	0	Setting a bit HIGH generates a channel event pulse for the selected channel. Write: 1 = channel event pulse generated for one CTICLK period 0 = no effect. There is one bit of the register for each channel.

4.14.6.6 CM7_CM7CTI_CTIINEN

Description: CTI Trigger to Channel Enable Registers
Address: 0xE0042020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger to Channel Enable Registers enable the signalling of an event on CTM channels when the core issues a trigger, CTITRIGIN, to the CTI. There is one register for each of the eight CTITRIGIN inputs. Within each register there is one bit for each of the four channels implemented. These registers do not affect the application trigger operations.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGINEN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGINEN	RW	RW	0	Enables a cross trigger event to the corresponding channel when an CTITRIGIN is activated. 1 = enables the CTITRIGIN signal to generate an event on the respective channel of the CTM. There is one bit of the register for each of the four channels. For example in register CTIINEN0, TRIGINEN[0] set to 1 enables CTITRIGIN onto channel 0. 0 = disables the CTITRIGIN signal from generating an event on the respective channel of the CTM.

4.14.6.7 CM7_CM7CTI_CTIOUTEN

Description: CTI Channel to Trigger Enable Registers

Address: 0xE00420A0

Offset: 0xA0

Retention: Retained

IsDeepSleep: No

Comment: The CTI Channel to Trigger Enable Registers define which channels can generate a CTITRIGOUT output. There is one register for each of the eight CTITRIGOUT outputs. Within each register there is one bit for each of the four channels implemented. These registers affect the mapping from application trigger to trigger outputs.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGOUTEN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGOUTEN	RW	RW	0	Changing the value of this bit from a 0 to a 1 enables a channel event for the corresponding channel to generate an CTITRIGOUT output: 0 = the channel input (CTICHIN) from the CTM is not routed to the CTITRIGOUT output 1 = the channel input (CTICHIN) from the CTM is routed to the CTITRIGOUT output. There is one bit for each of the four channels. For example in register CTIOUTEN0, enabling bit 0 enables CTICHIN[0] to cause a trigger event on the CTITRIGOUT[0] output.

4.14.6.8 CM7_CM7CTI_CTITRIGINSTATUS

Description: CTI Trigger In Status Register
Address: 0xE0042130
Offset: 0x130
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger In Status Register provides the status of the CTITRIGIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGINSTATUS [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGINSTATUS	R	R	0	Shows the status of the CTITRIGIN inputs: 1 = CTITRIGIN is active 0 = CTITRIGIN is inactive. Because the register provides a view of the raw CTITRIGIN inputs, the reset value is unknown. There is one bit of the register for each trigger input.

4.14.6.9 CM7_CM7CTI_CTITRIGOUTSTATUS

Description: CTI Trigger Out Status Register
Address: 0xE0042134
Offset: 0x134
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger Out Status Register provides the status of the CTITRIGOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGOUTSTATUS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGOUTSTATUS	R	R	0	Shows the status of the CTITRIGOUT outputs. 1 = CTITRIGOUT is active 0 = CTITRIGOUT is inactive (reset). There is one bit of the register for each trigger output.

4.14.6.10 CM7_CM7CTI_CTICHINSTATUS

Description: CTI Channel In Status Register
Address: 0xE0042138
Offset: 0x138
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel In Status Register provides the status of the CTI CTICHIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHINSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHINSTATUS	R	R	0	Shows the status of the CTICHIN inputs: 1 = CTICHIN is active 0 = CTICHIN is inactive. Because the register provides a view of the raw CTICHIN inputs from the CTM, the reset value is unknown. There is one bit of the register for each channel input.

4.14.6.11 CM7_CM7CTI_CTICHOUTSTATUS

Description: CTI Channel Out Status Register
Address: 0xE004213C
Offset: 0x13C
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel Out Status Register provides the status of the CTI CTICHOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHOUTSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHOUTSTATUS	R	R	0	Shows the status of the CTICHOUT outputs. 1 = CTICHOUT is active 0 = CTICHOUT is inactive (reset). There is one bit of the register for each channel output.

4.14.6.12 CM7_CM7CTI_CTIGATE

Description: Enable CTI Channel Gate Register

Address: 0xE0042140

Offset: 0x140

Retention: Retained

IsDeepSleep: No

Comment: The Gate Enable Register prevents the channels from propagating through the CTM to other CTIs. This enables local cross-triggering, for example for causing an interrupt when the ETM trigger occurs. It can be used effectively with CTIAPPSET, CTIAPPCLEAR, and CTIAPPPULSE for asserting trigger outputs by asserting channels, without affecting the rest of the system. On reset, this register is 0xF, and channel propagation is enabled.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTIGATEEN3 [3:3]	CTIGATEEN2 [2:2]	CTIGATEEN1 [1:1]	CTIGATEEN0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTIGATEEN0	RW	RW	1	Enable CTICHOUT0. Set to 0 to disable channel propagation.
1	CTIGATEEN1	RW	RW	1	Enable CTICHOUT1. Set to 0 to disable channel propagation.
2	CTIGATEEN2	RW	RW	1	Enable CTICHOUT2. Set to 0 to disable channel propagation.
3	CTIGATEEN3	RW	RW	1	Enable CTICHOUT3. Set to 0 to disable channel propagation.

4.14.6.13 CM7_CM7CTI_ASICCTL

Description: External Multiplexor Control Register
Address: 0xE0042144
Offset: 0x144
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ASICCTL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ASICCTL	RW	RW	0	Implementation-defined ASIC control, value written to the register is output on ASICCTL[7:0]. If external multiplexing of trigger signals is implemented then the number of multiplexed signals on each trigger must be reflected within the Device ID Register. This is done within a Verilog define EXTMUXNUM. See ECT CoreSight defined registers on page 4-28.

4.14.6.14 CM7_CM7CTI_ITCHINACK

Description: ITCHINACK Register
Address: 0xE0042EDC
Offset: 0xEDC
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHINACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHINACK	W	W	0	Set the value of the CTCHINACK outputs

4.14.6.15 CM7_CM7CTI_ITTRIGINACK

Description: ITTRIGINACK Register
Address: 0xE0042EE0
Offset: 0xEE0
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGINACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGINACK	W	W	0	Set the value of the CTTRIGINACK outputs

4.14.6.16 CM7_CM7CTI_ITCHOUT

Description: ITCHOUT Register
Address: 0xE0042EE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUT [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUT	W	W	0	Set the value of the CTCHOUT outputs

4.14.6.17 CM7_CM7CTI_ITTRIGOUT

Description: ITTRIGOUT Register
Address: 0xE0042EE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUT	W	W	0	Set the value of the CTTRIGOUT outputs

4.14.6.18 CM7_CM7CTI_ITCHOUTACK

Description: ITCHOUTACK Register
Address: 0xE0042EEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUTACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUTACK	R	R	0	Read the values of the CTCHOUTACK inputs

4.14.6.19 CM7_CM7CTI_ITTRIGOUTACK

Description: ITTRIGOUTACK Register
Address: 0xE0042EF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUTACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUTACK	R	R	0	Read the values of the CTTRIGOUTACK inputs

4.14.6.20 CM7_CM7CTI_ITCHIN

Description: ITCHIN Register
Address: 0xE0042EF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHIN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHIN	R	R	0	Read the values of the CTCHIN inputs

4.14.6.21 CM7_CM7CTI_ITTRIGIN

Description: ITTRIGIN Register
Address: 0xE0042EF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGIN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGIN	R	R	0	Read the values of the CTTRIGIN inputs

4.14.6.22 CM7_CM7CTI_ITCTRL

Description: Integration Mode Control Register

Address: 0xE0042F00

Offset: 0xF00

Retention: Retained

IsDeepSleep: No

Comment: This register enables the component to switch from a functional mode, the default behavior, to integration mode where the inputs and outputs of the component can be directly controlled for the purpose of integration testing and topology solving.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MODE	RW	RW	0	When set, the component enters integration mode, enabling topology detection or integration testing to be performed. At reset the component must enter functional mode. If no integration functionality is implemented, this register must read as zero.

4.14.6.23 CM7_CM7CTI_CLAIMSET

Description: Claim Tag Set Register

Address: 0xE0042FA0

Offset: 0xFA0

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location allows individual bits to be set, write, and returns the number of bits that can be set, read.

You can determine how many claim bits are implemented by reading this register. For example, if 4 bits are implemented, a read of this register will return 0x0000000F. If no claim tag is implemented, then a read of this register will return 0x00000000.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1S	RW1S	15	A bit programmable register bank which sets the Claim Tag Value. A read will return a logic 1 for all implemented locations.

4.14.6.24 CM7_CM7CTI_CLAIMCLR

Description: Claim Tag Clear Register

Address: 0xE0042FA4

Offset: 0xFA4

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location enables individual bits to be cleared, write, and returns the current Claim Tag value, read. The width (n) of this register can be determined from reading the Claim Tag Set Register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1C	RW1C	0	A bit programmable register bank that is zero at reset.

4.14.6.25 CM7_CM7CTI_LOCKACCESS

Description: Lock Access Register

Address: 0xE0042FB0

Offset: 0xFB0

Retention: Retained

IsDeepSleep: No

Comment: This is used to enable write access to device registers. If LOCKSTATUS[0] == 0x0 then this register is not present.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ACCESS_CODE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ACCESS_CODE	RW	RW	0	Write Access Code. A write of 0xC5ACCE55 enables further write access to this device. An invalid write will have the affect of removing write access. If LOCKSTATUS[2] is set, then only bits [7:0] of this register are implemented and lock access is obtained by consecutively writing 0xC5, 0xAC, 0xCE, 0x55. Bits [31:8] are unused and any writes to them ignored.

4.14.6.26 CM7_CM7CTI_LOCKSTATUS

Description: Lock Status Register

Address: 0xE0042FB4

Offset: 0xFB4

Retention: Retained

IsDeepSleep: No

Comment: This indicates the status of the Lock control mechanism. This lock prevents accidental writes by code under debug.

This register must always be present although there might not be any lock-access control mechanism. The lock mechanism, where present and locked, must block write accesses to any control register, except the Lock Access Register. For most components this covers all registers except for the Lock Access Register 0xFB0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					IMPLEMENT S_8B [2:2]	ACCESS _PE MITTED [1:1]	EXISTS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EXISTS	R	R	0	Indicates that a lock control mechanism exists for this device
1	ACCESS_PERMITTED	R	R	0	The values of this bit mean: 0 = Access permitted. 1 = Write access to the component is blocked. All writes to control registers are ignored. Reads are permitted
2	IMPLEMENTS_8B	R	R	0	This component implements an 8-bit Lock Access Register.

4.14.6.28 CM7_CM7CTI_DEVID

Description: Device Configuration Register

Address: 0xE0042FC8

Offset: 0xFC8

Retention: Retained

IsDeepSleep: No

Comment: This register is implementation-defined for each Part Number and Designer. This indicates the capabilities of the component. The entire 32-bit field can be used because the data width is determined by the particular component. Unused bits must read as zero.
If the component is configurable then it is recommended that this register reflects any changes to a standard configuration.

Default: 0x40804

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			NRMUXING [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	NRTRIG [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				NRCHAN [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	NRMUXING	R	R	4	Indicates the number of multiplexing available on Trigger Inputs and Trigger Outputs using ASICCTL. Default value of 5'b00000 indicating no multiplexing present. Reflects the value of the Verilog `define EXTMUXNUM that you must alter accordingly.
8:15	NRTRIG	R	R	8	Number of ECT triggers available.
16:19	NRCHAN	R	R	4	Number of ECT channels available.

4.14.6.30 CM7_CM7CTI_PID4

Description: Peripheral Identification Register 4
Address: 0xE0042FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.6.31 CM7_CM7CTI_PID5

Description: Peripheral Identification Register 5
Address: 0xE0042FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.6.32 CM7_CM7CTI_PID6

Description: Peripheral Identification Register 6
Address: 0xE0042FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.6.33 CM7_CM7CTI_PID7

Description: Peripheral Identification Register 7
Address: 0xE0042FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.6.34 CM7_CM7CTI_PID0

Description: Peripheral Identification Register 0
Address: 0xE0042FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	6	N/A

4.14.6.35 CM7_CM7CTI_PID1

Description: Peripheral Identification Register 1
Address: 0xE0042FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	N/A

4.14.6.36 CM7_CM7CTI_PID2

Description: Peripheral Identification Register 2
Address: 0xE0042FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	43	N/A

4.14.6.37 CM7_CM7CTI_PID3

Description: Peripheral Identification Register 3
Address: 0xE0042FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision for MTB

4.14.6.38 CM7_CM7CTI_CID0

Description: Component Identification Register 0
Address: 0xE0042FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.6.39 CM7_CM7CTI_CID1

Description: Component Identification Register 1
Address: 0xE0042FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	N/A

4.14.6.40 CM7_CM7CTI_CID2

Description: Component Identification Register 2
Address: 0xE0042FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.6.41 CM7_CM7CTI_CID3

Description: Component Identification Register 3
Address: 0xE0042FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.7 TRCCTI

4.14.7.1 CM7_TRCCTI_CTICONTROL

Description: CTI Control Register
Address: 0xE0080000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: The CTI Control Register enables the CTI.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							GLBEN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GLBEN	RW	RW	0	Enables or disables the ECT: 0 = disabled (reset) 1 = enabled. When disabled, all cross triggering mapping logic functionality is disabled for this processor.

4.14.7.2 CM7_TRCCTI_CTIINTACK

Description: CTI Interrupt Acknowledge Register

Address: 0xE0080010

Offset: 0x10

Retention: Retained

IsDeepSleep: No

Comment: The CTI Interrupt Acknowledge Register is write-only. Any bits written as a 1 cause the CTITRIGOUT output signal to be acknowledged. The acknowledgement is cleared when MAPTRIGOUT is deactivated. This register is used when the CTITRIGOUT is used as a sticky output, that is, no hardware acknowledge is supplied, and a software acknowledge is required.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INTACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INTACK	W	W	0	Acknowledges the corresponding CTITRIGOUT output: 1 = CTITRIGOUT is acknowledged and is cleared when MAPTRIGOUT is LOW. 0 = no effect. There is one bit of the register for each CTITRIGOUT output.

4.14.7.3 CM7_TRCCTI_CTIAPPSET

Description: CTI Application Trigger Set Register
Address: 0xE0080014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Set Register is read/write. A write to this register causes a channel event to be raised, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPSET [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPSET	RW	RW	0	Setting a bit HIGH generates a channel event for the selected channel. Read: 0 = application trigger inactive (reset) 1 = application trigger active. Write: 0 = no effect 1 = generate channel event. There is one bit of the register for each channel.

4.14.7.4 CM7_TRCCTI_CTIAPPCLEAR

Description: CTI Application Trigger Clear Register
Address: 0xE0080018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment: The CTI Application Trigger Clear Register is write-only. A write to this register causes a channel event to be cleared, corresponding to the bit written to.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPCLEAR [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPCLEAR	W	W	0	Clears corresponding bits in the CTIAPPSET register. 1 = application trigger disabled in the CTIAPPSET register 0 = no effect. There is one bit of the register for each channel.

4.14.7.5 CM7_TRCCTI_CTIAPPPULSE

Description: CTI Application Pulse Register

Address: 0xE008001C

Offset: 0x1C

Retention: Retained

IsDeepSleep: No

Comment: The CTI Application Pulse Register is write-only. A write to this register causes a channel event pulse, one CTICLK period, to be generated, corresponding to the bit written to. The pulse external to the ECT can be extended to multi-cycle by the handshaking interface circuits. This register clears itself immediately, so it can be repeatedly written to without software having to clear it.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				APPULSE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	APPULSE	W	W	0	Setting a bit HIGH generates a channel event pulse for the selected channel. Write: 1 = channel event pulse generated for one CTICLK period 0 = no effect. There is one bit of the register for each channel.

4.14.7.6 CM7_TRCCTI_CTIINEN

Description: CTI Trigger to Channel Enable Registers
Address: 0xE0080020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger to Channel Enable Registers enable the signalling of an event on CTM channels when the core issues a trigger, CTITRIGIN, to the CTI. There is one register for each of the eight CTITRIGIN inputs. Within each register there is one bit for each of the four channels implemented. These registers do not affect the application trigger operations.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGINEN [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGINEN	RW	RW	0	Enables a cross trigger event to the corresponding channel when an CTITRIGIN is activated. 1 = enables the CTITRIGIN signal to generate an event on the respective channel of the CTM. There is one bit of the register for each of the four channels. For example in register CTIINEN0, TRIGINEN[0] set to 1 enables CTITRIGIN onto channel 0. 0 = disables the CTITRIGIN signal from generating an event on the respective channel of the CTM.

4.14.7.7 CM7_TRCCTI_CTIOUTEN

Description: CTI Channel to Trigger Enable Registers

Address: 0xE00800A0

Offset: 0xA0

Retention: Retained

IsDeepSleep: No

Comment: The CTI Channel to Trigger Enable Registers define which channels can generate a CTITRIGOUT output. There is one register for each of the eight CTITRIGOUT outputs. Within each register there is one bit for each of the four channels implemented. These registers affect the mapping from application trigger to trigger outputs.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TRIGOUTEN [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TRIGOUTEN	RW	RW	0	Changing the value of this bit from a 0 to a 1 enables a channel event for the corresponding channel to generate an CTITRIGOUT output: 0 = the channel input (CTICHIN) from the CTM is not routed to the CTITRIGOUT output 1 = the channel input (CTICHIN) from the CTM is routed to the CTITRIGOUT output. There is one bit for each of the four channels. For example in register CTIOUTEN0, enabling bit 0 enables CTICHIN[0] to cause a trigger event on the CTITRIGOUT[0] output.

4.14.7.8 CM7_TRCCTI_CTITRIGINSTATUS

Description: CTI Trigger In Status Register
Address: 0xE0080130
Offset: 0x130
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger In Status Register provides the status of the CTITRIGIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGINSTATUS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGINSTATUS	R	R	0	Shows the status of the CTITRIGIN inputs: 1 = CTITRIGIN is active 0 = CTITRIGIN is inactive. Because the register provides a view of the raw CTITRIGIN inputs, the reset value is unknown. There is one bit of the register for each trigger input.

4.14.7.9 CM7_TRCCTI_CTITRIGOUTSTATUS

Description: CTI Trigger Out Status Register
Address: 0xE0080134
Offset: 0x134
Retention: Retained
IsDeepSleep: No
Comment: The CTI Trigger Out Status Register provides the status of the CTITRIGOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGOUTSTATUS [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGOUTSTATUS	R	R	0	Shows the status of the CTITRIGOUT outputs. 1 = CTITRIGOUT is active 0 = CTITRIGOUT is inactive (reset). There is one bit of the register for each trigger output.

4.14.7.10 CM7_TRCCTI_CTICHINSTATUS

Description: CTI Channel In Status Register
Address: 0xE0080138
Offset: 0x138
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel In Status Register provides the status of the CTI CTICHIN inputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHINSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHINSTATUS	R	R	0	Shows the status of the CTICHIN inputs: 1 = CTICHIN is active 0 = CTICHIN is inactive. Because the register provides a view of the raw CTICHIN inputs from the CTM, the reset value is unknown. There is one bit of the register for each channel input.

4.14.7.11 CM7_TRCCTI_CTICHOUTSTATUS

Description: CTI Channel Out Status Register
Address: 0xE008013C
Offset: 0x13C
Retention: Retained
IsDeepSleep: No
Comment: The CTI Channel Out Status Register provides the status of the CTI CTICHOUT outputs.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTICHOUTSTATUS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTICHOUTSTATUS	R	R	0	Shows the status of the CTICHOUT outputs. 1 = CTICHOUT is active 0 = CTICHOUT is inactive (reset). There is one bit of the register for each channel output.

4.14.7.12 CM7_TRCCTI_CTIGATE

Description: Enable CTI Channel Gate Register

Address: 0xE0080140

Offset: 0x140

Retention: Retained

IsDeepSleep: No

Comment: The Gate Enable Register prevents the channels from propagating through the CTM to other CTIs. This enables local cross-triggering, for example for causing an interrupt when the ETM trigger occurs. It can be used effectively with CTIAPPSET, CTIAPPCLEAR, and CTIAPPPULSE for asserting trigger outputs by asserting channels, without affecting the rest of the system. On reset, this register is 0xF, and channel propagation is enabled.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTIGATEEN3 [3:3]	CTIGATEEN2 [2:2]	CTIGATEEN1 [1:1]	CTIGATEEN0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTIGATEEN0	RW	RW	1	Enable CTICHOUT0. Set to 0 to disable channel propagation.
1	CTIGATEEN1	RW	RW	1	Enable CTICHOUT1. Set to 0 to disable channel propagation.
2	CTIGATEEN2	RW	RW	1	Enable CTICHOUT2. Set to 0 to disable channel propagation.
3	CTIGATEEN3	RW	RW	1	Enable CTICHOUT3. Set to 0 to disable channel propagation.

4.14.7.13 CM7_TRCCTL_ASICCTL

Description: External Multiplexor Control Register
Address: 0xE0080144
Offset: 0x144
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ASICCTL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ASICCTL	RW	RW	0	Implementation-defined ASIC control, value written to the register is output on ASICCTL[7:0]. If external multiplexing of trigger signals is implemented then the number of multiplexed signals on each trigger must be reflected within the Device ID Register. This is done within a Verilog define EXTMUXNUM. See ECT CoreSight defined registers on page 4-28.

4.14.7.14 CM7_TRCCTI_ITCHINACK

Description: ITCHINACK Register
Address: 0xE0080EDC
Offset: 0xEDC
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHINACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHINACK	W	W	0	Set the value of the CTCHINACK outputs

4.14.7.15 CM7_TRCCTI_ITTRIGINACK

Description: ITTRIGINACK Register
Address: 0xE0080EE0
Offset: 0xEE0
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGINACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGINACK	W	W	0	Set the value of the CTTRIGINACK outputs

4.14.7.16 CM7_TRCCTI_ITCHOUT

Description: ITCHOUT Register
Address: 0xE0080EE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUT [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUT	W	W	0	Set the value of the CTCHOUT outputs

4.14.7.17 CM7_TRCCTI_ITTRIGOUT

Description: ITTRIGOUT Register
Address: 0xE0080EE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment: This register is a write-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUT	W	W	0	Set the value of the CTTRIGOUT outputs

4.14.7.18 CM7_TRCCTI_ITCHOUTACK

Description: ITCHOUTACK Register
Address: 0xE0080EEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHOUTACK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHOUTACK	R	R	0	Read the values of the CTCHOUTACK inputs

4.14.7.19 CM7_TRCCTI_ITTRIGOUTACK

Description: ITTRIGOUTACK Register
Address: 0xE0080EF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGOUTACK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGOUTACK	R	R	0	Read the values of the CTTRIGOUTACK inputs

4.14.7.20 CM7_TRCCTI_ITCHIN

Description: ITCHIN Register
Address: 0xE0080EF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CTCHIN [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CTCHIN	R	R	0	Read the values of the CTCHIN inputs

4.14.7.21 CM7_TRCCTI_ITTRIGIN

Description: ITTRIGIN Register
Address: 0xE0080EF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment: This register is a read-only register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CTTRIGIN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CTTRIGIN	R	R	0	Read the values of the CTTRIGIN inputs

4.14.7.22 CM7_TRCCTI_ITCTRL

Description: Integration Mode Control Register

Address: 0xE0080F00

Offset: 0xF00

Retention: Retained

IsDeepSleep: No

Comment: This register enables the component to switch from a functional mode, the default behavior, to integration mode where the inputs and outputs of the component can be directly controlled for the purpose of integration testing and topology solving.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MODE	RW	RW	0	When set, the component enters integration mode, enabling topology detection or integration testing to be performed. At reset the component must enter functional mode. If no integration functionality is implemented, this register must read as zero.

4.14.7.23 CM7_TRCCTI_CLAIMSET

Description: Claim Tag Set Register

Address: 0xE0080FA0

Offset: 0xFA0

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location allows individual bits to be set, write, and returns the number of bits that can be set, read.

You can determine how many claim bits are implemented by reading this register. For example, if 4 bits are implemented, a read of this register will return 0x0000000F. If no claim tag is implemented, then a read of this register will return 0x00000000.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1S	RW1S	15	A bit programmable register bank which sets the Claim Tag Value. A read will return a logic 1 for all implemented locations.

4.14.7.24 CM7_TRCCTI_CLAIMCLR

Description: Claim Tag Clear Register

Address: 0xE0080FA4

Offset: 0xFA4

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location enables individual bits to be cleared, write, and returns the current Claim Tag value, read. The width (n) of this register can be determined from reading the Claim Tag Set Register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1C	RW1C	0	A bit programmable register bank that is zero at reset.

4.14.7.25 CM7_TRCCTI_LOCKACCESS

Description: Lock Access Register

Address: 0xE0080FB0

Offset: 0xFB0

Retention: Retained

IsDeepSleep: No

Comment: This is used to enable write access to device registers. If LOCKSTATUS[0] == 0x0 then this register is not present.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ACCESS_CODE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ACCESS_CODE	RW	RW	0	Write Access Code. A write of 0xC5ACCE55 enables further write access to this device. An invalid write will have the affect of removing write access. If LOCKSTATUS[2] is set, then only bits [7:0] of this register are implemented and lock access is obtained by consecutively writing 0xC5, 0xAC, 0xCE, 0x55. Bits [31:8] are unused and any writes to them ignored.

4.14.7.26 CM7_TRCCTI_LOCKSTATUS

Description: Lock Status Register

Address: 0xE0080FB4

Offset: 0xFB4

Retention: Retained

IsDeepSleep: No

Comment: This indicates the status of the Lock control mechanism. This lock prevents accidental writes by code under debug.

This register must always be present although there might not be any lock-access control mechanism. The lock mechanism, where present and locked, must block write accesses to any control register, except the Lock Access Register. For most components this covers all registers except for the Lock Access Register 0xFB0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					IMPLEMENT S_8B [2:2]	ACCESS _PE MITTED [1:1]	EXISTS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EXISTS	R	R	0	Indicates that a lock control mechanism exists for this device
1	ACCESS_PERMITTED	R	R	0	The values of this bit mean: 0 = Access permitted. 1 = Write access to the component is blocked. All writes to control registers are ignored. Reads are permitted
2	IMPLEMENTS_8B	R	R	0	This component implements an 8-bit Lock Access Register.

4.14.7.28 CM7_TRCCTI_DEVID

Description: Device Configuration Register

Address: 0xE0080FC8

Offset: 0xFC8

Retention: Retained

IsDeepSleep: No

Comment: This register is implementation-defined for each Part Number and Designer. This indicates the capabilities of the component. The entire 32-bit field can be used because the data width is determined by the particular component. Unused bits must read as zero.
If the component is configurable then it is recommended that this register reflects any changes to a standard configuration.

Default: 0x40804

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			NRMUXING [4:0]				
Bits	15	14	13	12	11	10	9	8
Name	NRTRIG [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				NRCHAN [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	NRMUXING	R	R	4	Indicates the number of multiplexing available on Trigger Inputs and Trigger Outputs using ASICCTL. Default value of 5'b00000 indicating no multiplexing present. Reflects the value of the Verilog `define EXTMUXNUM that you must alter accordingly.
8:15	NRTRIG	R	R	8	Number of ECT triggers available.
16:19	NRCHAN	R	R	4	Number of ECT channels available.

4.14.7.29 CM7_TRCCTI_DEVTYPE

Description: Device Type Identifier Register
Address: 0xE0080FCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment: 0x14 indicates this device has a major type of debug control logic component (0x4) and sub-type corresponding to cross trigger (0x1).
Default: 0x14

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUB_TYPE [7:4]				CLASS [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CLASS	R	R	4	debug control logic component
4:7	SUB_TYPE	R	R	1	cross trigger

4.14.7.30 CM7_TRCCTI_PID4

Description: Peripheral Identification Register 4
Address: 0xE0080FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	N/A

4.14.7.31 CM7_TRCCTI_PID5

Description: Peripheral Identification Register 5
Address: 0xE0080FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.7.32 CM7_TRCCTI_PID6

Description: Peripheral Identification Register 6
Address: 0xE0080FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.7.33 CM7_TRCCTI_PID7

Description: Peripheral Identification Register 7
Address: 0xE0080FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	N/A

4.14.7.34 CM7_TRCCTI_PID0

Description: Peripheral Identification Register 0
Address: 0xE0080FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	6	N/A

4.14.7.35 CM7_TRCCTL_PID1

Description: Peripheral Identification Register 1
Address: 0xE0080FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	N/A

4.14.7.36 CM7_TRCCTI_PID2

Description: Peripheral Identification Register 2
Address: 0xE0080FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	43	N/A

4.14.7.37 CM7_TRCCTI_PID3

Description: Peripheral Identification Register 3
Address: 0xE0080FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	ECO revision for MTB

4.14.7.38 CM7_TRCCTL_CID0

Description: Component Identification Register 0
Address: 0xE0080FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	N/A

4.14.7.39 CM7_TRCCTL_CID1

Description: Component Identification Register 1
Address: 0xE0080FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	N/A

4.14.7.40 CM7_TRCCTL_CID2

Description: Component Identification Register 2
Address: 0xE0080FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	N/A

4.14.7.41 CM7_TRCCTL_CID3

Description: Component Identification Register 3
Address: 0xE0080FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	N/A

4.14.8 ETB_CSTF

4.14.8.1 TRC_CSTF

4.14.8.1.1 CM7_ETB_CSTF_CSTFCTL

Description: Funnel Control Register
Address: 0xE008C000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description: http://infocenter.arm.com/help/index.jsp?topic=/com.arm.doc.100536_0302_01_en/index.html

4.14.8.1.2 CM7_ETB_CSTF_CSTFCTL

Description: Priority Control Register
Address: 0xE008C004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.3 CM7_ETB_CSTF_ITATBDATA0

Description: Integration Register
Address: 0xE008CEEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.4 CM7_ETB_CSTF_ITATBCTR2

Description: Integration Register
Address: 0xE008CEF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.5 CM7_ETB_CSTF_ITATBCTR1

Description: Integration Register
Address: 0xE008CEF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.6 CM7_ETB_CSTF_ITATBCTR0

Description: Integration Register
Address: 0xE008CEF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.7 CM7_ETB_CSTF_ITCTRL

Description: Integration Mode Control Register
Address: 0xE008CF00
Offset: 0xF00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.8 CM7_ETB_CSTF_CLAIMSET

Description: Claim Tag Set Register
Address: 0xE008CFA0
Offset: 0xFA0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.9 CM7_ETB_CSTF_CLAIMCLR

Description: Claim Tag Clear Register
Address: 0xE008CFA4
Offset: 0xFA4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.10 CM7_ETB_CSTF_LOCKACCESS

Description: Lock Access Register
Address: 0xE008CFB0
Offset: 0xFB0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.11 CM7_ETB_CSTF_LOCKSTATUS

Description: Lock Status Register
Address: 0xE008CFB4
Offset: 0xFB4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.12 CM7_ETB_CSTF_AUTHSTATUS

Description: Authentication Status Register
Address: 0xE008CFB8
Offset: 0xFB8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.13 CM7_ETB_CSTF_DEVID

Description: Device ID
Address: 0xE008CFC8
Offset: 0xFC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.14 CM7_ETB_CSTF_DEVTYPE

Description: Device Type Identifier Register
Address: 0xE008CFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.15 CM7_ETB_CSTF_PID4

Description: Peripheral Identification Register 4
Address: 0xE008CFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.16 CM7_ETB_CSTF_PID5

Description: Peripheral Identification Register 5
Address: 0xE008CFD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.17 CM7_ETB_CSTF_PID6

Description: Peripheral Identification Register 6
Address: 0xE008CFD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.18 CM7_ETB_CSTF_PID7

Description: Peripheral Identification Register 7
Address: 0xE008CFDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.19 CM7_ETB_CSTF_PID0

Description: Peripheral Identification Register 0
Address: 0xE008CFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	6	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.20 CM7_ETB_CSTF_PID1

Description: Peripheral Identification Register 1
Address: 0xE008CFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.21 CM7_ETB_CSTF_PID2

Description: Peripheral Identification Register 2
Address: 0xE008CFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	43	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.22 CM7_ETB_CSTF_PID3

Description: Peripheral Identification Register 3
Address: 0xE008CFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.23 CM7_ETB_CSTF_CID0

Description: Component Identification Register 0
Address: 0xE008CFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.24 CM7_ETB_CSTF_CID1

Description: Component Identification Register 1
Address: 0xE008CFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.25 CM7_ETB_CSTF_CID2

Description: Component Identification Register 2
Address: 0xE008CFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.8.1.26 CM7_ETB_CSTF_CID3

Description: Component Identification Register 3
Address: 0xE008CFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9 ETB

4.14.9.1 CM7_ETB_ETBRDP

Description: RAM Depth Register
Address: 0xE008D004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.2 CM7_ETB_ETBSTS

Description: Status Register
Address: 0xE008D00C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.3 CM7_ETB_ETBRRD

Description: RAM Read Data Register
Address: 0xE008D010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.4 CM7_ETB_ETBRRP

Description: RAM Read Pointer Register
Address: 0xE008D014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.5 CM7_ETB_ETBRWP

Description: RAM Write Pointer Register
Address: 0xE008D018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.6 CM7_ETB_ETBTRG

Description: Trigger Counter Register
Address: 0xE008D01C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.7 CM7_ETB_ETBCTL

Description: Control Register
Address: 0xE008D020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.8 CM7_ETB_ETBRWD

Description: RAM Write Data Register
Address: 0xE008D024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.9 CM7_ETB_ETBFFSR

Description: Formatter and Flush Status Register
Address: 0xE008D300
Offset: 0x300
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.10 CM7_ETB_ETBFFCR

Description: Formatter and Flush Control Register
Address: 0xE008D304
Offset: 0x304
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.11 CM7_ETB_ITMISCOP0

Description: Integration Register
Address: 0xE008DEE0
Offset: 0xEE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.12 CM7_ETB_ITTRFLINACK

Description: Integration Register
Address: 0xE008DEE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.13 CM7_ETB_ITTRFLIN

Description: Integration Register
Address: 0xE008DEE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.14 CM7_ETB_ITATBDATA0

Description: Integration Register
Address: 0xE008DEEC
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.15 CM7_ETB_ITATBCTR2

Description: Integration Register
Address: 0xE008DEF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.16 CM7_ETB_ITATBCTR1

Description: Integration Register
Address: 0xE008DEF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.17 CM7_ETB_ITATBCTR0

Description: Integration Register
Address: 0xE008DEF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.18 CM7_ETB_ITCTRL

Description: Integration Mode Control Register
Address: 0xE008DF00
Offset: 0xF00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.19 CM7_ETB_CLAIMSET

Description: Claim Tag Set Register

Address: 0xE008DFA0

Offset: 0xFA0

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location allows individual bits to be set, write, and returns the number of bits that can be set, read.

You can determine how many claim bits are implemented by reading this register. For example, if 4 bits are implemented, a read of this register will return 0x0000000F. If no claim tag is implemented, then a read of this register will return 0x00000000.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1S	RW1S	15	A bit programmable register bank which sets the Claim Tag Value. A read will return a logic 1 for all implemented locations.

4.14.9.20 CM7_ETB_CLAIMCLR

Description: Claim Tag Clear Register

Address: 0xE008DFA4

Offset: 0xFA4

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location enables individual bits to be cleared, write, and returns the current Claim Tag value, read. The width (n) of this register can be determined from reading the Claim Tag Set Register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1C	RW1C	0	A bit programmable register bank that is zero at reset.

4.14.9.21 CM7_ETB_LOCKACCESS

Description: Lock Access Register

Address: 0xE008DFB0

Offset: 0xFB0

Retention: Retained

IsDeepSleep: No

Comment: This is used to enable write access to device registers. If LOCKSTATUS[0] == 0x0 then this register is not present.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ACCESS_CODE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ACCESS_CODE	RW	RW	0	Write Access Code. A write of 0xC5ACCE55 enables further write access to this device. An invalid write will have the affect of removing write access. If LOCKSTATUS[2] is set, then only bits [7:0] of this register are implemented and lock access is obtained by consecutively writing 0xC5, 0xAC, 0xCE, 0x55. Bits [31:8] are unused and any writes to them ignored.

4.14.9.22 CM7_ETB_LOCKSTATUS

Description: Lock Status Register

Address: 0xE008DFB4

Offset: 0xFB4

Retention: Retained

IsDeepSleep: No

Comment: This indicates the status of the Lock control mechanism. This lock prevents accidental writes by code under debug.

This register must always be present although there might not be any lock-access control mechanism. The lock mechanism, where present and locked, must block write accesses to any control register, except the Lock Access Register. For most components this covers all registers except for the Lock Access Register 0xFB0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					IMPLEMENT S_8B [2:2]	ACCESS _PE MITTED [1:1]	EXISTS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EXISTS	R	R	0	Indicates that a lock control mechanism exists for this device
1	ACCESS_PERMITTED	R	R	0	The values of this bit mean: 0 = Access permitted. 1 = Write access to the component is blocked. All writes to control registers are ignored. Reads are permitted
2	IMPLEMENTS_8B	R	R	0	This component implements an 8-bit Lock Access Register.

4.14.9.24 CM7_ETB_DEVID

Description: Device ID
Address: 0xE008DFC8
Offset: 0xFC8
Retention: Retained
IsDeepSleep: No
Comment: This register is implementation-defined for each Part Number and Designer. This indicates the capabilities of the component. The entire 32-bit field can be used because the data width is determined by the particular component. Unused bits must read as zero.
 If the component is configurable then it is recommended that this register reflects any changes to a standard configuration.
Default: 0x40804

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			NRMUXING [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	NRTRIG [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				NRCHAN [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	NRMUXING	R	R	4	Indicates the number of multiplexing available on Trigger Inputs and Trigger Outputs using ASICCTL. Default value of 5'b00000 indicating no multiplexing present. Reflects the value of the Verilog `define EXTMUXNUM that you must alter accordingly.
8:15	NRTRIG	R	R	8	Number of ECT triggers available.
16:19	NRCHAN	R	R	4	Number of ECT channels available.

4.14.9.25 CM7_ETB_DEVTYPE

Description: Device Type Identifier Register
Address: 0xE008DFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment: Indicates device type
Default: 0x12

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUB_TYPE [7:4]				CLASS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CLASS	R	R	2	debug control logic component
4:7	SUB_TYPE	R	R	1	cross trigger

4.14.9.26 CM7_ETB_PID4

Description: Peripheral Identification Register 4
Address: 0xE008DFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.27 CM7_ETB_PID5

Description: Peripheral Identification Register 5
Address: 0xE008DFD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.28 CM7_ETB_PID6

Description: Peripheral Identification Register 6
Address: 0xE008DFD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.29 CM7_ETB_PID7

Description: Peripheral Identification Register 7
Address: 0xE008DFDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.30 CM7_ETB_PID0

Description: Peripheral Identification Register 0
Address: 0xE008DFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	6	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.31 CM7_ETB_PID1

Description: Peripheral Identification Register 1
Address: 0xE008DFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.32 CM7_ETB_PID2

Description: Peripheral Identification Register 2
Address: 0xE008DFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	43	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.33 CM7_ETB_PID3

Description: Peripheral Identification Register 3
Address: 0xE008DFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.34 CM7_ETB_CID0

Description: Component Identification Register 0
Address: 0xE008DFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.35 CM7_ETB_CID1

Description: Component Identification Register 1
Address: 0xE008DFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.36 CM7_ETB_CID2

Description: Component Identification Register 2
Address: 0xE008DFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.9.37 CM7_ETB_CID3

Description: Component Identification Register 3
Address: 0xE008DFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Refer CoreSight TRM for details of register description. See link in TRC_CSTF.CSTFCTL register.

4.14.10 TPIU

4.14.10.1 CM7_TPIU_TPIU_SPSR

Description: Supported Port Size Register
Address: 0xE008E000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	1	Refer CM7 TRM and CoreSight TRM for register descriptions: CoreSight TRM: https://svn.design.cypress.com:18080/viewvc/chips/trunk/s40/MXS40/Platform/MXS40-SAS/SupportFiles/ARM_docs/CoreSight/DDI0480G_coresight_soc_r3p2_trm.pdf?revision=69465&view=markup CM7 TRM : http://infocenter.arm.com/help/index.jsp?topic=/com.arm.doc.ddi0489f/index.html

4.14.10.2 CM7_TPIU_TPIU_CPSR

Description: Current Port Size Register
Address: 0xE008E004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	1	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.3 CM7_TPIU_TPIU_STMR

Description: Supported Trigger Modes Register
Address: 0xE008E100
Offset: 0x100
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x11F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	287	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.4 CM7_TPIU_TPIU_TCVR

Description: Trigger Counter Value Register
Address: 0xE008E104
Offset: 0x104
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.5 CM7_TPIU_TPIU_TMR

Description: Trigger Multiplier register
Address: 0xE008E108
Offset: 0x108
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.6 CM7_TPIU_TPIU_STPMR

Description: Supported Test Patterns/Modes register
Address: 0xE008E200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3000F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	196623	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.7 CM7_TPIU_TPIU_CTPMR

Description: Current Test Pattern/Modes register
Address: 0xE008E204
Offset: 0x204
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.8 CM7_TPIU_TPIU_TPCR

Description: TPIU Test Pattern Repeat Counter Register
Address: 0xE008E208
Offset: 0x208
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.9 CM7_TPIU_TPIU_FFSR

Description: Formatter and Flush Status Register
Address: 0xE008E300
Offset: 0x300
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.10 CM7_TPIU_TPIU_FFCR

Description: Formatter and Flush Control Register
Address: 0xE008E304
Offset: 0x304
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.11 CM7_TPIU_TPIU_FSCR

Description: Formatter Synchronization Counter Register
Address: 0xE008E308
Offset: 0x308
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	64	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.12 CM7_TPIU_TPIU_EXCTLIPR

Description: TPIU EXCTL In Port Register
Address: 0xE008E400
Offset: 0x400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.13 CM7_TPIU_TPIU_EXCTLPR

Description: TPIU EXCTL Out Port register
Address: 0xE008E404
Offset: 0x404
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.14 CM7_TPIU_ITTRFLINACK

Description: Integration Test Trigger In and Flush In Acknowledge register
Address: 0xE008EEE4
Offset: 0xEE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.15 CM7_TPIU_ITTRFLIN

Description: Integration Test Trigger In and Flush In register
Address: 0xE008EEE8
Offset: 0xEE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.16 CM7_TPIU_ITATBDATA0

Description: Integration Test ATB Data register 0
Address: 0xE008EEEE
Offset: 0xEEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.17 CM7_TPIU_ITATBCTR2

Description: Integration Test ATB Control Register 2
Address: 0xE008EEF0
Offset: 0xEF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.18 CM7_TPIU_ITATBCTR1

Description: Integration Test ATB Control Register 1
Address: 0xE008EEF4
Offset: 0xEF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.19 CM7_TPIU_ITATBCTR0

Description: Integration Test ATB Control Register 0
Address: 0xE008EEF8
Offset: 0xEF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	RW	RW	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.20 CM7_TPIU_ITCTRL

Description: Integration Mode Control register

Address: 0xE008EF00

Offset: 0xF00

Retention: Retained

IsDeepSleep: No

Comment: This register enables the component to switch from a functional mode, the default behavior, to integration mode where the inputs and outputs of the component can be directly controlled for the purpose of integration testing and topology solving.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MODE	RW	RW	0	When set, the component enters integration mode, enabling topology detection or integration testing to be performed. At reset the component must enter functional mode. If no integration functionality is implemented, this register must read as zero.

4.14.10.21 CM7_TPIU_CLAIMSET

Description: Claim Tag Set Register

Address: 0xE008EFA0

Offset: 0xFA0

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location allows individual bits to be set, write, and returns the number of bits that can be set, read.
You can determine how many claim bits are implemented by reading this register. For example, if 4 bits are implemented, a read of this register will return 0x0000000F. If no claim tag is implemented, then a read of this register will return 0x00000000.

Default: 0xF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1S	RW1S	15	A bit programmable register bank which sets the Claim Tag Value. A read will return a logic 1 for all implemented locations.

4.14.10.22 CM7_TPIU_CLAIMCLR

Description: Claim Tag Clear Register

Address: 0xE008EFA4

Offset: 0xFA4

Retention: Retained

IsDeepSleep: No

Comment: This register forms one half of the Claim Tag value. This location enables individual bits to be cleared, write, and returns the current Claim Tag value, read. The width (n) of this register can be determined from reading the Claim Tag Set Register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TAG [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TAG	RW1C	RW1C	0	A bit programmable register bank that is zero at reset.

4.14.10.23 CM7_TPIU_LOCKACCESS

Description: Lock Access Register

Address: 0xE008EFB0

Offset: 0xFB0

Retention: Retained

IsDeepSleep: No

Comment: This is used to enable write access to device registers. If LOCKSTATUS[0] == 0x0 then this register is not present.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ACCESS_CODE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ACCESS_CODE	RW	RW	0	Write Access Code. A write of 0xC5ACCE55 enables further write access to this device. An invalid write will have the affect of removing write access. If LOCKSTATUS[2] is set, then only bits [7:0] of this register are implemented and lock access is obtained by consecutively writing 0xC5, 0xAC, 0xCE, 0x55. Bits [31:8] are unused and any writes to them ignored.

4.14.10.24 CM7_TPIU_LOCKSTATUS

Description: Lock Status Register

Address: 0xE008EFB4

Offset: 0xFB4

Retention: Retained

IsDeepSleep: No

Comment: This indicates the status of the Lock control mechanism. This lock prevents accidental writes by code under debug.

This register must always be present although there might not be any lock-access control mechanism. The lock mechanism, where present and locked, must block write accesses to any control register, except the Lock Access Register. For most components this covers all registers except for the Lock Access Register 0xFB0.

Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					NTT [2:2]	SLK [1:1]	SLI [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLI	R	R	1	Software Lock Implemented. Indicates that a lock control mechanism is present from this interface. 0 Indicates that a lock control mechanism is not present from this interface. Write operations to the LAR are ignored. 1 Indicates that a lock control mechanism is present from this interface.
1	SLK	R	R	1	Software Lock Status. Returns the present lock status of the device, from the current interface. 0 Indicates that write operations are permitted from this interface. 1 Indicates that write operations are not permitted from this interface. Read operations are permitted.
2	NTT	R	R	0	Register size indicator. Always 0. Indicates that the LAR is implemented as 32-bit.

4.14.10.26 CM7_TPIU_DEVID

Description: Device Configuration register

Address: 0xE008EFC8

Offset: 0xFC8

Retention: Retained

IsDeepSleep: No

Comment: This register is implementation-defined for each Part Number and Designer. This indicates the capabilities of the component. The entire 32-bit field can be used because the data width is determined by the particular component. Unused bits must read as zero.
If the component is configurable then it is recommended that this register reflects any changes to a standard configuration.

Default: 0xA0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name			CLKRELAT [5:5]	MUXNUM [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				SWOUARTNRZ [11:11]	SWOMAN [10:10]	TCLKDATA [9:9]	FIFOSIZE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	MUXNUM	R	R	0	Indicates the hidden level of input multiplexing. When non-zero, this value indicates the type of multiplexing on the input to the ATB. Currently only 0x00 is supported, that is, no multiplexing is present. This value helps detect the ATB structure.
5	CLKRELAT	R	R	1	Indicates the relationship between atclk and traceclk. 1: atclk and traceclk are asynchronous.
6:8	FIFOSIZE	R	R	2	FIFO size in powers of 2. 0b010: FIFO size of 4 entries, that is, 16 bytes.
9	TCLKDATA	R	R	0	Indicates whether trace clock plus data is supported. 0: Trace clock and data is supported.
10	SWOMAN	R	R	0	Indicates whether Serial Wire Output, Manchester encoded format, is supported. 0: Serial Wire Output, Manchester encoded format, is not supported.
11	SWOUARTNRZ	R	R	0	Indicates whether Serial Wire Output, UART or NRZ, is supported. 0: Serial Wire Output, UART or NRZ, is not supported.

4.14.10.27 CM7_TPIU_DEVTYPE

Description: Device Type Identifier register
Address: 0xE008EFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment: Indicates device type
Default: 0x11

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUB [7:4]				MAJOR [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	MAJOR	R	R	1	Major classification of the type of the debug component as specified in the ARM(R) CoreSight(TM) Architecture Specification for this debug and trace component. 0b0001: Indicates that this component is a trace sink component.
4:7	SUB	R	R	1	Sub-classification of the type of the debug component as specified in the ARM(R) CoreSight(TM) Architecture Specification within the major classification as specified in the MAJOR field. 0b0001: Indicates that this component is a trace port component.

4.14.10.28 CM7_TPIU_PID4

Description: Peripheral Identification Register 4
Address: 0xE008EFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.29 CM7_TPIU_PID0

Description: Peripheral Identification Register 0
Address: 0xE008EFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x12

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	18	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.30 CM7_TPIU_PID1

Description: Peripheral Identification Register 1
Address: 0xE008EFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	185	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.31 CM7_TPIU_PID2

Description: Peripheral Identification Register 2
Address: 0xE008EFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4B

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	75	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.32 CM7_TPIU_PID3

Description: Peripheral Identification Register 3
Address: 0xE008EFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECOREVNUM [7:4]				None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:7	ECOREVNUM	R	R	0	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.33 CM7_TPIU_CID0

Description: Component Identification Register 0
Address: 0xE008EFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.34 CM7_TPIU_CID1

Description: Component Identification Register 1
Address: 0xE008EFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x90

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	144	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.35 CM7_TPIU_CID2

Description: Component Identification Register 2
Address: 0xE008EFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.10.36 CM7_TPIU_CID3

Description: Component Identification Register 3
Address: 0xE008E0FC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Refer DDI0480G ARM Coresight Soc-400 TRM Section 3.12 for register descriptions

4.14.11 ROMTABLE

4.14.11.1 CM7_ROMTABLE_TRC_CTI

Description: CM7 CoreSight ROM Table Peripheral #0
Address: 0xE00BF000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFC1003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429470925 1	Offset to TRC CTI ROM Table

4.14.11.2 CM7_ROMTABLE_TRC_TRC_CSTF

Description: CM7 CoreSight ROM Table Peripheral #1
Address: 0xE00BF004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFCD003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4294758403	Offset to CSTF ROM Table

4.14.11.3 CM7_ROMTABLE_TRC_ETB

Description: CM7 CoreSight ROM Table Peripheral #2
Address: 0xE00BF008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFCE003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429476249 9	Offset to ETB ROM Table

4.14.11.4 CM7_ROMTABLE_TRC_TPIU

Description: CM7 CoreSight ROM Table Peripheral #3
Address: 0xE00BF00C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFCF003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429476659 5	Offset to TPIU ROM Table

4.14.11.5 CM7_ROMTABLE_TRC_CSMT

Description: CM7 CoreSight ROM Table Memory Type
Address: 0xE00BFFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Memory Type

4.14.11.6 CM7_ROMTABLE_TRC_PID4

Description: CM7 CoreSight ROM Table Peripheral ID #4
Address: 0xE00BFFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

4.14.11.7 CM7_ROMTABLE_TRC_PID0

Description: CM7 CoreSight ROM Table Peripheral ID #0
Address: 0xE00BFFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	192	Peripheral ID #0

4.14.11.8 CM7_ROMTABLE_TRC_PID1

Description: CM7 CoreSight ROM Table Peripheral ID #1
Address: 0xE00BFFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	180	Peripheral ID #1

4.14.11.9 CM7_ROMTABLE_TRC_PID2

Description: CM7 CoreSight ROM Table Peripheral ID #2
Address: 0xE00BFFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

4.14.11.10 CM7_ROMTABLE_TRC_PID3

Description: CM7 CoreSight ROM Table Peripheral ID #3
Address: 0xE00BFFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

4.14.11.11 CM7_ROMTABLE_TRC_CID0

Description: CM7 CoreSight ROM Table Component ID #0
Address: 0xE00BFFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

4.14.11.12 CM7_ROMTABLE_TRC_CID1

Description: CM7 CoreSight ROM Table Component ID #1
Address: 0xE00BFFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component ID #1

4.14.11.13 CM7_ROMTABLE_TRC_CID2

Description: CM7 CoreSight ROM Table Component ID #2
Address: 0xE00BFFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

4.14.11.14 CM7_ROMTABLE_TRC_CID3

Description: CM7 CoreSight ROM Table Component ID #3
Address: 0xE00BFFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

4.14.12 ROMTABLE

4.14.12.1 CM7_ROMTABLE_CM7

Description: CM7 CoreSight ROM Table Peripheral #0
Address: 0xE00FE000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4099	Offset to CM7 ROM Table

4.14.12.2 CM7_ROMTABLE_CM7_ETM

Description: CM7 CoreSight ROM Table Peripheral #1
Address: 0xE00FE004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF43003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429419315 5	Offset to ETM ROM Table

4.14.12.3 CM7_ROMTABLE_CM7_CTI

Description: CM7 CoreSight ROM Table Peripheral #2
Address: 0xE00FE008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF44003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429419725 1	Offset to CTI ROM Table

4.14.12.4 CM7_ROMTABLE_DBG_TRC_ROM

Description: CM7 CoreSight ROM Table Peripheral #3
Address: 0xE00FE010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFC1003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429470925 1	Offset to DBG_TRC ROM Table

4.14.12.5 CM7_ROMTABLE_CSMT

Description: CM7 CoreSight ROM Table Memory Type
Address: 0xE00FEFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Memory Type

4.14.12.6 CM7_ROMTABLE_PID4

Description: CM7 CoreSight ROM Table Peripheral ID #4
Address: 0xE00FEFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

4.14.12.7 CM7_ROMTABLE_PID0

Description: CM7 CoreSight ROM Table Peripheral ID #0
Address: 0xE00FEFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	192	Peripheral ID #0

4.14.12.8 CM7_ROMTABLE_PID1

Description: CM7 CoreSight ROM Table Peripheral ID #1
Address: 0xE00FEFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	180	Peripheral ID #1

4.14.12.9 CM7_ROMTABLE_PID2

Description: CM7 CoreSight ROM Table Peripheral ID #2
Address: 0xE00FEFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

4.14.12.10 CM7_ROMTABLE_PID3

Description: CM7 CoreSight ROM Table Peripheral ID #3
Address: 0xE00FEFEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

4.14.12.11 CM7_ROMTABLE_CID0

Description: CM7 CoreSight ROM Table Component ID #0
Address: 0xE00FEFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

4.14.12.12 CM7_ROMTABLE_CID1

Description: CM7 CoreSight ROM Table Component ID #1
Address: 0xE00FEFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component ID #1

4.14.12.13 CM7_ROMTABLE_CID2

Description: CM7 CoreSight ROM Table Component ID #2
Address: 0xE00FEFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

4.14.12.14 CM7_ROMTABLE_CID3

Description: CM7 CoreSight ROM Table Component ID #3
Address: 0xE00FEFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

4.14.13 ROM

4.14.13.1 CM7_ROM_SCS

Description: CM7 CoreSight ROM Table Peripheral #0
Address: 0xE00FF000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF0F003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429398016 3	Offset to SCS ROM Table

4.14.13.2 CM7_ROM_DWT

Description: CM7 CoreSight ROM Table Peripheral #1
Address: 0xE00FF004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF02003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4293926915	Offset to DWT ROM Table

4.14.13.3 CM7_ROM_FPB

Description: CM7 CoreSight ROM Table Peripheral #2
Address: 0xE00FF008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF03003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	429393101 1	Offset to FPB ROM Table

4.14.13.4 CM7_ROM_ITM

Description: CM7 CoreSight ROM Table Peripheral #3
Address: 0xE00FF00C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF01003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4293922819	Offset to ITM ROM Table

4.14.13.5 CM7_ROM_CSMT

Description: CM7 CoreSight ROM Table Memory Type
Address: 0xE00FFFCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	Memory Type

4.14.13.6 CM7_ROM_PID4

Description: CM7 CoreSight ROM Table Peripheral ID #4
Address: 0xE00FFFD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	4	Peripheral ID #4

4.14.13.7 CM7_ROM_PID0

Description: CM7 CoreSight ROM Table Peripheral ID #0
Address: 0xE00FFFE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC7

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	199	Peripheral ID #0

4.14.13.8 CM7_ROM_PID1

Description: CM7 CoreSight ROM Table Peripheral ID #1
Address: 0xE00FFFE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	180	Peripheral ID #1

4.14.13.9 CM7_ROM_PID2

Description: CM7 CoreSight ROM Table Peripheral ID #2
Address: 0xE00FFE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	11	Peripheral ID #2

4.14.13.10 CM7_ROM_PID3

Description: CM7 CoreSight ROM Table Peripheral ID #3
Address: 0xE00FFFE0
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	Peripheral ID #3

4.14.13.11 CM7_ROM_CID0

Description: CM7 CoreSight ROM Table Component ID #0
Address: 0xE00FFFF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component ID #0

4.14.13.12 CM7_ROM_CID1

Description: CM7 CoreSight ROM Table Component ID #1
Address: 0xE00FFFF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component ID #1

4.14.13.13 CM7_ROM_CID2

Description: CM7 CoreSight ROM Table Component ID #2
Address: 0xE00FFF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component ID #2

4.14.13.14 CM7_ROM_CID3

Description: CM7 CoreSight ROM Table Component ID #3
Address: 0xE00FFFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component ID #3

5 CPUSS

Description CPU subsystem (CPUSS)
Base Address 0x40200000
Size 0x10000
Slave Num MMIO2 - 0

Register Name	Address	Permission	Description
CPUSS_IDENTITY	0x40200000	FULL	Identity
CPUSS_CM7_0_STATUS	0x40200004	FULL	CM7 0 status
CPUSS_FAST_0_CLOCK_CTL	0x40200008	FULL	Fast 0 clock control
CPUSS_CM7_0_CTL	0x4020000C	FULL	CM7 0 control
CPUSS_CM7_0_INT_STATUS0	0x40200100	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS1	0x40200104	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS2	0x40200108	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS3	0x4020010C	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS4	0x40200110	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS5	0x40200114	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS6	0x40200118	FULL	CM7 0 interrupt status
CPUSS_CM7_0_INT_STATUS7	0x4020011C	FULL	CM7 0 interrupt status
CPUSS_CM7_0_VECTOR_TABLE_BASE	0x40200200	FULL	CM7 0 vector table base
CPUSS_CM7_0_NMI_CTL0	0x40200240	FULL	CM7 0 NMI control
CPUSS_CM7_0_NMI_CTL1	0x40200244	FULL	CM7 0 NMI control
CPUSS_CM7_0_NMI_CTL2	0x40200248	FULL	CM7 0 NMI control
CPUSS_CM7_0_NMI_CTL3	0x4020024C	FULL	CM7 0 NMI control
CPUSS_TRC_DBG_CLOCK_CTL	0x40200320	FULL	Trace and debug clock control
CPUSS_CM7_1_STATUS	0x40200404	FULL	CM7 1 status
CPUSS_FAST_1_CLOCK_CTL	0x40200408	FULL	Fast 1 clock control
CPUSS_CM7_1_CTL	0x4020040C	FULL	CM7 1 control
CPUSS_CM7_1_INT_STATUS0	0x40200500	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS1	0x40200504	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS2	0x40200508	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS3	0x4020050C	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS4	0x40200510	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS5	0x40200514	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS6	0x40200518	FULL	CM7 1 interrupt status
CPUSS_CM7_1_INT_STATUS7	0x4020051C	FULL	CM7 1 interrupt status
CPUSS_CM7_1_VECTOR_TABLE_BASE	0x40200600	FULL	CM7 1 vector table base
CPUSS_CM7_1_NMI_CTL0	0x40200640	FULL	CM7 1 NMI control
CPUSS_CM7_1_NMI_CTL1	0x40200644	FULL	CM7 1 NMI control
CPUSS_CM7_1_NMI_CTL2	0x40200648	FULL	CM7 1 NMI control
CPUSS_CM7_1_NMI_CTL3	0x4020064C	FULL	CM7 1 NMI control
CPUSS_CM0_CTL	0x40201000	FULL	CM0+ control
CPUSS_CM0_STATUS	0x40201004	FULL	CM0+ status
CPUSS_SLOW_CLOCK_CTL	0x40201008	FULL	Slow clock control
CPUSS_PERI_CLOCK_CTL	0x4020100C	FULL	Peripheral interconnect clock control
CPUSS_MEM_CLOCK_CTL	0x40201010	FULL	Memory clock control
CPUSS_CM0_INT0_STATUS	0x40201100	FULL	CM0+ interrupt 0 status
CPUSS_CM0_INT1_STATUS	0x40201104	FULL	CM0+ interrupt 1 status
CPUSS_CM0_INT2_STATUS	0x40201108	FULL	CM0+ interrupt 2 status
CPUSS_CM0_INT3_STATUS	0x4020110C	FULL	CM0+ interrupt 3 status
CPUSS_CM0_INT4_STATUS	0x40201110	FULL	CM0+ interrupt 4 status
CPUSS_CM0_INT5_STATUS	0x40201114	FULL	CM0+ interrupt 5 status
CPUSS_CM0_INT6_STATUS	0x40201118	FULL	CM0+ interrupt 6 status
CPUSS_CM0_INT7_STATUS	0x4020111C	FULL	CM0+ interrupt 7 status
CPUSS_CM0_VECTOR_TABLE_BASE	0x40201120	FULL	CM0+ vector table base
CPUSS_CM0_NMI_CTL0	0x40201140	FULL	CM0+ NMI control
CPUSS_CM0_NMI_CTL1	0x40201144	FULL	CM0+ NMI control
CPUSS_CM0_NMI_CTL2	0x40201148	FULL	CM0+ NMI control
CPUSS_CM0_NMI_CTL3	0x4020114C	FULL	CM0+ NMI control
CPUSS_CM7_0_PWR_CTL	0x40201200	FULL	CM7 0 power control
CPUSS_CM7_0_PWR_DELAY_CTL	0x40201204	FULL	CM7 0 power delay control
CPUSS_CM7_1_PWR_CTL	0x40201210	FULL	CM7 1 power control

Register Name	Address	Permission	Description
CPUSS_CM7_1_PWR_DELAY_CTL	0x40201214	FULL	CM7 1 power delay control
CPUSS_RAM0_CTL0	0x40201300	FULL	RAM 0 control
CPUSS_RAM0_STATUS	0x40201304	FULL	RAM 0 status
CPUSS_RAM0_PWR_MACRO_CTL0	0x40201340	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL1	0x40201344	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL2	0x40201348	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL3	0x4020134C	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL4	0x40201350	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL5	0x40201354	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL6	0x40201358	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL7	0x4020135C	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL8	0x40201360	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL9	0x40201364	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL10	0x40201368	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL11	0x4020136C	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL12	0x40201370	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL13	0x40201374	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL14	0x40201378	FULL	RAM 0 power control
CPUSS_RAM0_PWR_MACRO_CTL15	0x4020137C	FULL	RAM 0 power control
CPUSS_RAM1_CTL0	0x40201380	FULL	RAM 1 control
CPUSS_RAM1_STATUS	0x40201384	FULL	RAM 1 status
CPUSS_RAM1_PWR_CTL	0x40201388	FULL	RAM 1 power control
CPUSS_RAM_PWR_DELAY_CTL	0x402013C0	FULL	Power up delay used for all SRAM power domains
CPUSS_ROM_CTL	0x402013C4	FULL	ROM control
CPUSS_ECC_CTL	0x402013C8	FULL	ECC control
CPUSS_PRODUCT_ID	0x40201400	FULL	Product identifier and version (same as CoreSight RomTables)
CPUSS_DP_STATUS	0x40201410	FULL	Debug port status
CPUSS_AP_CTL	0x40201414	FULL	Access port control
CPUSS_BUFF_CTL	0x40201500	FULL	Buffer control
CPUSS_SYSTICK_CTL	0x40201600	FULL	SysTick timer control
CPUSS_CAL_SUP_SET	0x40201800	FULL	Calibration support set and read
CPUSS_CAL_SUP_CLR	0x40201804	FULL	Calibration support clear and reset
CPUSS_CM0_PC_CTL	0x40202000	READ	CM0+ protection context control
CPUSS_CM0_PC0_HANDLER	0x40202040	READ	CM0+ protection context 0 handler
CPUSS_CM0_PC1_HANDLER	0x40202044	READ	CM0+ protection context 1 handler
CPUSS_CM0_PC2_HANDLER	0x40202048	READ	CM0+ protection context 2 handler
CPUSS_CM0_PC3_HANDLER	0x4020204C	READ	CM0+ protection context 3 handler
CPUSS_PROTECTION	0x402020C4	READ	Protection status
CPUSS_TRIM_ROM_CTL	0x40202100	READ	ROM trim control
CPUSS_TRIM_RAM_CTL	0x40202104	READ	RAM trim control for less than 100MHz SRAMs
CPUSS_TRIM_RAM200_CTL	0x40202108	READ	RAM trim control for 100MHz - 200MHz SRAMs
CPUSS_TRIM_RAM350_CTL	0x4020210C	READ	RAM trim control for more than 200MHz SRAMs
CPUSS_CM0_SYSTEM_INT_CTL0	0x40208000	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL1	0x40208004	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL2	0x40208008	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL3	0x4020800C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL4	0x40208010	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL5	0x40208014	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL6	0x40208018	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL7	0x4020801C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL8	0x40208020	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL9	0x40208024	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL10	0x40208028	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL11	0x4020802C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL12	0x40208030	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL13	0x40208034	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL14	0x40208038	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL15	0x4020803C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL16	0x40208040	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL17	0x40208044	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL18	0x40208048	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL19	0x4020804C	FULL	CM0+ system interrupt control

Technical Reference Manual	775	002-33817 Rev. ** 2021-10-22

Technical Reference Manual	776	002-33817 Rev. ** 2021-10-22

Technical Reference Manual 777 002-33817 Rev. **
2021-10-22

Technical Reference Manual	778	002-33817 Rev. ** 2021-10-22

Technical Reference Manual	779	002-33817 Rev. ** 2021-10-22

Technical Reference Manual	780	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
CPUSS_CM0_SYSTEM_INT_CTL398	0x40208638	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL399	0x4020863C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL400	0x40208640	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL401	0x40208644	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL402	0x40208648	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL403	0x4020864C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL404	0x40208650	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL405	0x40208654	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL406	0x40208658	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL407	0x4020865C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL408	0x40208660	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL409	0x40208664	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL410	0x40208668	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL411	0x4020866C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL412	0x40208670	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL413	0x40208674	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL414	0x40208678	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL415	0x4020867C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL416	0x40208680	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL417	0x40208684	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL418	0x40208688	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL419	0x4020868C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL420	0x40208690	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL421	0x40208694	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL422	0x40208698	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL423	0x4020869C	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL424	0x402086A0	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL425	0x402086A4	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL426	0x402086A8	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL427	0x402086AC	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL428	0x402086B0	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL429	0x402086B4	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL430	0x402086B8	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL431	0x402086BC	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL432	0x402086C0	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL433	0x402086C4	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL434	0x402086C8	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL435	0x402086CC	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL436	0x402086D0	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL437	0x402086D4	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL438	0x402086D8	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL439	0x402086DC	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL440	0x402086E0	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL441	0x402086E4	FULL	CM0+ system interrupt control
CPUSS_CM0_SYSTEM_INT_CTL442	0x402086E8	FULL	CM0+ system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL0	0x4020A000	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL1	0x4020A004	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL2	0x4020A008	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL3	0x4020A00C	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL4	0x4020A010	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL5	0x4020A014	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL6	0x4020A018	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL7	0x4020A01C	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL8	0x4020A020	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL9	0x4020A024	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL10	0x4020A028	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL11	0x4020A02C	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL12	0x4020A030	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL13	0x4020A034	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL14	0x4020A038	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL15	0x4020A03C	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL16	0x4020A040	FULL	CM7 0 system interrupt control
CPUSS_CM7_0_SYSTEM_INT_CTL17	0x4020A044	FULL	CM7 0 system interrupt control

Technical Reference Manual	782	002-33817 Rev. ** 2021-10-22

Technical Reference Manual 783 002-33817 Rev. **
2021-10-22

Technical Reference Manual	784	002-33817 Rev. ** 2021-10-22

Technical Reference Manual 785 002-33817 Rev. **
2021-10-22

Technical Reference Manual	786	002-33817 Rev. ** 2021-10-22

Technical Reference Manual	787	002-33817 Rev. ** 2021-10-22

Technical Reference Manual 788 002-33817 Rev. **
2021-10-22

Technical Reference Manual 789 002-33817 Rev. **
2021-10-22

Technical Reference Manual 790 002-33817 Rev. **
2021-10-22

Technical Reference Manual	791	002-33817 Rev. ** 2021-10-22

Technical Reference Manual 792 002-33817 Rev. **
2021-10-22

Technical Reference Manual 793 002-33817 Rev. **
2021-10-22

Technical Reference Manual 794 002-33817 Rev. **
2021-10-22

Register Name	Address	Permission	Description
CPUSS_CM7_1_SYSTEM_INT_CTL394	0x4020C628	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL395	0x4020C62C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL396	0x4020C630	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL397	0x4020C634	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL398	0x4020C638	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL399	0x4020C63C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL400	0x4020C640	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL401	0x4020C644	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL402	0x4020C648	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL403	0x4020C64C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL404	0x4020C650	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL405	0x4020C654	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL406	0x4020C658	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL407	0x4020C65C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL408	0x4020C660	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL409	0x4020C664	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL410	0x4020C668	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL411	0x4020C66C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL412	0x4020C670	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL413	0x4020C674	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL414	0x4020C678	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL415	0x4020C67C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL416	0x4020C680	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL417	0x4020C684	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL418	0x4020C688	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL419	0x4020C68C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL420	0x4020C690	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL421	0x4020C694	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL422	0x4020C698	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL423	0x4020C69C	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL424	0x4020C6A0	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL425	0x4020C6A4	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL426	0x4020C6A8	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL427	0x4020C6AC	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL428	0x4020C6B0	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL429	0x4020C6B4	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL430	0x4020C6B8	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL431	0x4020C6BC	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL432	0x4020C6C0	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL433	0x4020C6C4	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL434	0x4020C6C8	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL435	0x4020C6CC	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL436	0x4020C6D0	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL437	0x4020C6D4	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL438	0x4020C6D8	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL439	0x4020C6DC	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL440	0x4020C6E0	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL441	0x4020C6E4	FULL	CM7 1 system interrupt control
CPUSS_CM7_1_SYSTEM_INT_CTL442	0x4020C6E8	FULL	CM7 1 system interrupt control

5.1 Register Details

5.1.1 CPUSS_IDENTITY

Description: Identity
Address: 0x40200000
Offset: 0x0
Retention: Not Retained
IsDeepSleep: No
Comment: This register is typically used by SW that is executed on different bus masters or with different protection contexts.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:2]		NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				MS [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	R	R	Undefined	This field specifies the privileged setting ('0': user mode; '1': privileged mode) of the transfer that reads the register.
1	NS	R	R	Undefined	This field specifies the security setting ('0': secure mode; '1': non-secure mode) of the transfer that reads the register.
4:7	PC	R	R	Undefined	This field specifies the protection context of the transfer that reads the register.
8:11	MS	R	R	Undefined	This field specifies the bus master identifier of the transfer that reads the register.

5.1.2 CPUSS_CM7_0_STATUS

Description: CM7 0 status
Address: 0x40200004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x13

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PWR_DONE [4:4]	None [3:2]		SLEEPDEEP [1:1]	SLEEPING [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			TCMC_AHB_MS [12:12]	TCMC_EXT_MS_3 [11:11]	TCMC_EXT_MS_2_TO_0 [10:10]	TCMC_CM7_1_MS [9:9]	None [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLEEPING	R	R	1	Specifies if the CPU is in Active, Sleep or DeepSleep power mode: - Active power mode: SLEEPING is '0'. - Sleep power mode: SLEEPING is '1' and SLEEPDEEP is '0'. - DeepSleep power mode: SLEEPING is '1' and SLEEPDEEP is '1'.
1	SLEEPDEEP	R	R	1	Specifies if the CPU is in Sleep or DeepSleep power mode. See SLEEPING field.
4	PWR_DONE	R	R	1	After a PWR_MODE change this flag indicates if the new power mode has taken effect or not. Note: this flag can also change as a result of a change in debug power up req
9	TCMC_CM7_1_MS	R	R	0	Outstanding transactions from CM7 1. '0': There are no outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from CM7 1. '1': There are outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from CM7 1. Do not switch the CM7 power off.
10	TCMC_EXT_MS_2_TO_0	R	R	0	Outstanding transactions from external AXI masters 2 to 0. '0': There are no outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from external AXI masters 2 to 0. '1': There are outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from external AXI masters 2 to 0. Do not switch the CM7 power off.

Bits	Name	SW	HW	Default or Enum	Description
11	TCMC_EXT_MS_3	R	R	0	Outstanding transactions from external AXI master 3. '0': There are no outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from external AXI master 3. '1': There are outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from external AXI master 3. Do not switch the CM7 power off.
12	TCMC_AHB_MS	R	R	0	Ongoing AHB transaction. '0': There is no ongoing transaction to the CM7 I/D-TCM slave port (AHBS) from an AHB master. '1': There is an ongoing transaction to the CM7 I/D-TCM slave port (AHBS) from an AHB master. Do not switch the CM7 power off.

5.1.3 CPUSS_FAST_0_CLOCK_CTL

Description: Fast 0 clock control

Address: 0x40200008

Offset: 0x8

Retention: Retained

IsDeepSleep: No

Comment: Clock division control to divide and generate clk_fast_0 from clk_hf<x>. Note that this register is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

Note that CM7 clocks must be running before accessing this register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FRAC_DIV [7:3]						None [2:0]	

Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3:7	FRAC_DIV	RW	RW	0	Fractional division by (FRAC_DIV/32). Allows for fractional divisions in the range [0, 31/32]. Note that fractional division results in clock jitter as some clock periods may be 1 'clk_hf<x>' cycle longer than other clock periods.
8:15	INT_DIV	RW	RW	0	Integer division by (1+INT_DIV). Allows for integer divisions in the range [1, 256] (INT_DIV is in the range [0, 255]).

5.1.4 CPUSS_CM7_0_CTL

Description: CM7 0 control
Address: 0x4020000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			CPU_WAIT [4:4]	PPB_LOCK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				INIT_RMW_EN [11:10]		INIT_TCM_EN [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	TCMC_EN [23:23]	DTCM_READ_WS [22:22]	DTCM_ECC_INJ_EN [21:21]	DTCM_ECC_EN [20:20]	ITCM_ECC_CHECK_DIS [19:19]	ITCM_READ_WS [18:18]	ITCM_ECC_INJ_EN [17:17]	ITCM_ECC_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	IDC_MASK [31:31]	None [30:29]		IXC_MASK [28:28]	UFC_MASK [27:27]	OFC_MASK [26:26]	DZC_MASK [25:25]	IOC_MASK [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PPB_LOCK	RW	RW	15	Write disable for specific CPU registers: Bit 0: ITCMR register. '0': enabled; '1': disabled. Bit 1: DTCMR register. '0': enabled; '1': disabled. Bit 2: AHBPCR register. '0': enabled; '1': disabled. Bit 3: VTOR register. '0': enabled; '1': disabled.
4	CPU_WAIT	RW	RW	1	When this signal is '1' out of reset, it forces the CPU into a quiescent state that delays its boot-up sequence and instruction execution until this signal is driven '0'. This allows the TCMs to be loaded by the system before the CPU performs any TCM accesses. The CPU AHBS interface functions while CPU_WAIT is '1' and services transactions initiated by the system (e.g. DMA controller) to load the TCMs.
8:9	INIT_TCM_EN	RW	RW	0	TCM enable initialization after reset: Bit 0: ITCM. '0': disabled; '1': enabled. Bit 1: DTCM. '0': disabled; '1': enabled.
10:11	INIT_RMW_EN	RW	RW	0	TCM read-modify-write enable initialization after reset: Bit 0: ITCM. '0': disabled; '1': enabled. Bit 1: DTCM. '0': disabled; '1': enabled. Note: When TCM ECC is enabled, the read-modify-write functionality should be enabled. This prevents partial (sub-word) writes to the TCM.
16	ITCM_ECC_EN	RW	RW	0	ITCM ECC enable: '0': Disabled. '1': Enabled.
17	ITCM_ECC_INJ_EN	RW	RW	0	ITCM ECC error injection enable: '0': Disabled. '1': Enabled.

Bits	Name	SW	HW	Default or Enum	Description
18	ITCM_READ_WS	RW	RW	0	ITCM read wait states (writes have no wait states). '0': 0 wait states. '1': 1 wait state.
19	ITCM_ECC_CHECK_DIS	RW	RW	0	Disable ECC checking and thus fault reports. This also disables ECC correction (required to enable initialization). Intended usage is initialization. This bit is ignored when TCM_ECC_EN=0.
20	DTCM_ECC_EN	RW	RW	0	DTCM ECC enable: '0': Disabled. '1': Enabled.
21	DTCM_ECC_INJ_EN	RW	RW	0	DTCM ECC error injection enable: '0': Disabled. '1': Enabled.
22	DTCM_READ_WS	RW	RW	0	DTCM read wait states (writes have no wait states). '0': 0 wait states. '1': 1 wait state.
23	TCMC_EN	RW	RW	0	CM7 TCMC access control: '0': Disable access to the CM7 I/D-TCM slave port (AHBS). Access attempts will get a bus error response. '1': Enable access to the CM7 I/D-TCM slave port (AHBS). Before switching the CM7 power off, set this field to 0, and confirm that there are no outstanding AXI transactions and no ongoing AHB transactions to the CM7 TCMs, by checking that bits TCMC_* in CM7_x_STATUS are '0'.
24	IOC_MASK	RW	RW	0	CPU floating point unit (FPU) exception mask for the CPU's FPCSR.IOC 'invalid operation' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt. Note: the ARM architecture does NOT support FPU exceptions; i.e. there is no precise FPU exception handler. Instead, FPU conditions are captured in the CPU's FPCSR register and the conditions are provided as CPU interface signals. The interface signals are 'masked' with the fields a provide by this register (CM7_0_CTL). The 'masked' signals are reduced/OR-ed into a single CPU floating point interrupt signal. The associated CPU interrupt handler allows for imprecise handling of FPU exception conditions. Note: the CPU's FPCSR exception conditions are 'sticky'. Typically, the CPU FPU interrupt handler will clear the exception condition(s) to '0'. Note: by default, the FPU exception masks are '0'. Therefore, FPU exception conditions will NOT activate the CPU's floating point interrupt.
25	DZC_MASK	RW	RW	0	CPU FPU exception mask for the CPU's FPCSR.DZC 'divide by zero' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt.

Bits	Name	SW	HW	Default or Enum	Description
26	OFC_MASK	RW	RW	0	CPU FPU exception mask for the CPU's FPCSR.OFC 'overflow' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt.
27	UFC_MASK	RW	RW	0	CPU FPU exception mask for the CPU's FPCSR.UFC 'underflow' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt.
28	IXC_MASK	RW	RW	0	CPU FPU exception mask for the CPU's FPCSR.IXC 'inexact' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt. Note: the 'inexact' condition is set as a result of rounding. Rounding may occur frequently and is typically not an error condition. To prevent frequent CPU FPU interrupts as a result of rounding, this field is typically set to '0'.
31	IDC_MASK	RW	RW	0	CPU FPU exception mask for the CPU's FPCSR.IDC 'input denormalized' exception condition: '0': The CPU's exception condition does NOT activate the CPU's floating point interrupt. '1': the CPU's exception condition activates the CPU's floating point interrupt. Note: if the CPU FPCSR.FZ field is set to '1', denormalized inputs are 'flushed to zero'. Dependent on the FPU algorithm, this may or may not occur frequently. To prevent frequent CPU FPU interrupts as a result of denormalized inputs, this field may be set to '0'.

5.1.5 CPUSS_CM7_0_INT_STATUS

Description: CM7 0 interrupt status
Address: 0x40200100
Offset: 0x100
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM7_0 activated system interrupt index for CPU interrupt. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.6 CPUSS_CM7_0_VECTOR_TABLE_BASE

Description: CM7 0 vector table base
Address: 0x40200200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [6:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR25 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR25 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR25 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
7:31	ADDR25	RW	RW	131072	The default CM7 vector table base address is 0x0100:0000 (CM7 VTOR and reset exception handler address after reset). This is the location of the system ROM memory. The system ROM is mirrored at 0x0000:0000. This is required for the CM0+ boot process (the CM0+ VTOR and reset exception handler address is at fixed address 0x0000:0000 after reset). The system ROM requires mirroring as the CM7 CPUs' ITCMs are located at base address 0x0000:0000 and effectively cut a hole in the system ROM mirror address space (but the 0x0100:0000 address space is not affected).

5.1.7 CPUSS_CM7_0_NMI_CTL

Description: CM7 0 NMI control

Address: 0x40200240

Offset: 0x240

Retention: Retained

IsDeepSleep: No

Comment: Note that multiple (four) CM7_0_NMI_CTL registers exist, allowing for multiple (four) system interrupts to be connected to the CPU NMI. The four selected system interrupts are logically OR'd into a single CPU NMI input. The NMI handler may need to investigate all selected system interrupt sources to identify the source of CPU NMI.

Default: 0x3FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	RW	RW	1023	System interrupt select for CPU NMI. The reset value ('1023') ensures that the CPU NMI is NOT connected to any system interrupt after DeepSleep reset.

5.1.8 CPUSS_TRC_DBG_CLOCK_CTL

Description: Trace and debug clock control
Address: 0x40200320
Offset: 0x320
Retention: Retained
IsDeepSleep: No
Comment: Clock division control to divide and generate clk_trc_dbg from clk_hf0_dbg (clk_hf0_dbg is same as clk_hf0, but runs only when debugger is connected i.e when CDBGPWRUPREQ=1).
Default: 0x200

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	INT_DIV	RW	RW	2	Integer division by (1+INT_DIV). Allows for integer divisions in the range [1, 256] (INT_DIV is in the range [0, 255]). Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

5.1.9 CPUSS_CM7_1_STATUS

Description: CM7 1status
Address: 0x40200404
Offset: 0x404
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x13

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PWR_DONE [4:4]	None [3:2]		SLEEPDEEP [1:1]	SLEEPING [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			TCMC_AHB_MS [12:12]	TCMC_EXT_MS_3 [11:11]	TCMC_EXT_MS_2_TO_0 [10:10]	None [9:9]	TCMC_CM7_0_MS [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLEEPING	R	R	1	Specifies if the CPU is in Active, Sleep or DeepSleep power mode: - Active power mode: SLEEPING is '0'. - Sleep power mode: SLEEPING is '1' and SLEEPDEEP is '0'. - DeepSleep power mode: SLEEPING is '1' and SLEEPDEEP is '1'.
1	SLEEPDEEP	R	R	1	Specifies if the CPU is in Sleep or DeepSleep power mode. See SLEEPING field.
4	PWR_DONE	R	R	1	After a PWR_MODE change this flag indicates if the new power mode has taken effect or not. Note: this flag can also change as a result of a change in debug power up req
8	TCMC_CM7_0_MS	R	R	0	Outstanding transactions from CM7 0. '0': There are no outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from CM7 0. '1': There are outstanding transactions to the CM7 I/D-TCM slave port (AHBS) from CM7 0. Do not switch the CM7 power off.
10	TCMC_EXT_MS_2_TO_0	R	R	0	Refer CM7_0_STATUS description.
11	TCMC_EXT_MS_3	R	R	0	Refer CM7_0_STATUS description.
12	TCMC_AHB_MS	R	R	0	Refer CM7_0_STATUS description.

5.1.10 CPUSS_FAST_1_CLOCK_CTL

Description: Fast 1 clock control

Address: 0x40200408

Offset: 0x408

Retention: Retained

IsDeepSleep: No

Comment: Clock division control to divide and generate clk_fast_1 from clk_hf<x>. Note that this register is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.
Note that CM7 clocks must be running before accessing this register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FRAC_DIV [7:3]					None [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3:7	FRAC_DIV	RW	RW	0	Refer FAST_0_CLOCK_CTL description.
8:15	INT_DIV	RW	RW	0	Refer FAST_0_CLOCK_CTL description.

5.1.11 CPUSS_CM7_1_CTL

Description: CM7 1 control
Address: 0x4020040C
Offset: 0x40C
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			CPU_WAIT [4:4]	PPB_LOCK [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				INIT_RMW_EN [11:10]		INIT_TCM_EN [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	TCMC_EN [23:23]	DTCM_READ_WS [22:22]	DTCM_ECC_INJ_EN [21:21]	DTCM_ECC_EN [20:20]	ITCM_ECC_CHECK_DIS [19:19]	ITCM_READ_WS [18:18]	ITCM_ECC_INJ_EN [17:17]	ITCM_ECC_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	IDC_MASK [31:31]	None [30:29]		IXC_MASK [28:28]	UFC_MASK [27:27]	OFC_MASK [26:26]	DZC_MASK [25:25]	IOC_MASK [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PPB_LOCK	RW	RW	15	Refer CM7_0_CTL description.
4	CPU_WAIT	RW	RW	1	Refer CM7_0_CTL description.
8:9	INIT_TCM_EN	RW	RW	0	Refer CM7_0_CTL description.
10:11	INIT_RMW_EN	RW	RW	0	Refer CM7_0_CTL description.
16	ITCM_ECC_EN	RW	RW	0	Refer CM7_0_CTL description.
17	ITCM_ECC_INJ_EN	RW	RW	0	Refer CM7_0_CTL description.
18	ITCM_READ_WS	RW	RW	0	Refer CM7_0_CTL description.
19	ITCM_ECC_CHECK_DIS	RW	RW	0	Disable ECC checking and thus fault reports. This also disables ECC correction (required to enable initialization). Intended usage is initialization. This bit is ignored when TCM_ECC_EN=0.
20	DTCM_ECC_EN	RW	RW	0	Refer CM7_0_CTL description.
21	DTCM_ECC_INJ_EN	RW	RW	0	Refer CM7_0_CTL description.
22	DTCM_READ_WS	RW	RW	0	Refer CM7_0_CTL description.
23	TCMC_EN	RW	RW	0	Refer CM7_0_CTL description.
24	IOC_MASK	RW	RW	0	Refer CM7_0_CTL description.
25	DZC_MASK	RW	RW	0	Refer CM7_0_CTL description.
26	OFC_MASK	RW	RW	0	Refer CM7_0_CTL description.
27	UFC_MASK	RW	RW	0	Refer CM7_0_CTL description.
28	IXC_MASK	RW	RW	0	Refer CM7_0_CTL description.
31	IDC_MASK	RW	RW	0	Refer CM7_0_CTL description.

5.1.12 CPUSS_CM7_1_INT_STATUS

Description: CM7_1 interrupt status
Address: 0x40200500
Offset: 0x500
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM7_1 activated system interrupt index for CPU interrupt 0. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.13 CPUSS_CM7_1_VECTOR_TABLE_BASE

Description: CM7 1 vector table base
Address: 0x40200600
Offset: 0x600
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [6:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR25 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR25 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR25 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
7:31	ADDR25	RW	RW	131072	The default CM7 vector table base address is 0x0100:0000 (CM7 VTOR and reset exception handler address after reset). This is the location of the system ROM memory. The system ROM is mirrored at 0x0000:0000. This is required for the CM0+ boot process (the CM0+ VTOR and reset exception handler address is at fixed address 0x0000:0000 after reset). The system ROM requires mirroring as the CM7 CPUs' ITCMs are located at base address 0x0000:0000 and effectively cut a hole in the system ROM mirror address space (but the 0x0100:0000 address space is not affected).

5.1.14 CPUSS_CM7_1_NMI_CTL

Description: CM7 1 NMI control
Address: 0x40200640
Offset: 0x640
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	RW	RW	1023	Refer CM7_0_NMI_CTL description.

5.1.15 CPUSS_CM0_CTL

Description: CM0+ control
Address: 0x40201000
Offset: 0x1000
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFA050002

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						ENABLED [1:1]	SLV_STALL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLV_STALL	RW	RW	0	Processor debug access control: '0': Access. '1': Stall access. This field is used to stall/delay debug accesses. This is useful to protect execution of code that needs to be protected from debug accesses.
1	ENABLED	RW	RW	1	Processor enable: '0': Disabled. Processor clock is turned off and reset is activated. After SW clears this field to '0', HW automatically sets this field to '1'. This effectively results in a CM0+ reset, followed by a CM0+ warm boot. '1': Enabled. Note: The intent is that this bit is modified only through an external probe or by the CM7 while the CM0+ is in Sleep or DeepSleep power mode. If this field is cleared to '0' by the CM0+ itself, it should be done under controlled conditions (such that undesirable side effects can be prevented). Note: The CM0+ CPU has a AIRCR.SYSRESETREQ register field that allows the CM0+ to reset the complete device (ENABLED only disables/enables the CM0+), resulting in a warm boot. This CPU register field has similar 'built-in protection' as this CM0_CTL register to prevent accidental system writes (the upper 16-bits of the register need to be written with a 0x05fa key value; see CPU user manual for more details). Note: a CM0+ processor reset results in the reset of its associated protection context in MS_CTL (PC and PC_SAVED) to '0'.

Bits	Name	SW	HW	Default or Enum	Description
16:31	VECTKEYSTAT	R	R	64005	Register key (to prevent accidental writes). - Should be written with a 0x05fa key value for the write to take effect. - Always reads as 0xfa05. Note: Although the SW attribute for this field says "R", SW need to write the key 0x05fa in this field for this register write to happen. This is a built in protection provided to prevent accidental writes from SW.

5.1.16 CPUSS_CM0_STATUS

Description: CM0+ status
Address: 0x40201004
Offset: 0x1004
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						SLEEPDEEP [1:1]	SLEEPING [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLEEPING	R	R	0	Specifies if the CPU is in Active, Sleep or DeepSleep power mode: - Active power mode: SLEEPING is '0'. - Sleep power mode: SLEEPING is '1' and SLEEPDEEP is '0'. - DeepSleep power mode: SLEEPING is '1' and SLEEPDEEP is '1'.
1	SLEEPDEEP	R	R	0	Specifies if the CPU is in Sleep or DeepSleep power mode. See SLEEPING field.

5.1.17 CPUSS_SLOW_CLOCK_CTL

Description: Slow clock control
Address: 0x40201008
Offset: 0x1008
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	INT_DIV	RW	RW	0	Specifies the slow clock divider (from the memory/AXI clock 'clk_mem' to the slow clock 'clk_slow'). Integer division by (1+INT_DIV). Allows for integer divisions in the range [1, 256] (INT_DIV is in the range [0, 255]). Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

5.1.18 CPUSS_PERI_CLOCK_CTL

Description: Peripheral interconnect clock control
Address: 0x4020100C
Offset: 0x100C
Retention: Retained
IsDeepSleep: No
Comment: Clock division control to divide and generate clk_peri from clk_hf0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	INT_DIV	RW	RW	0	Integer division by (1+INT_DIV). Allows for integer divisions in the range [1, 256] (INT_DIV is in the range [0, 255]). Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

5.1.19 CPUSS_MEM_CLOCK_CTL

Description: Memory clock control
Address: 0x40201010
Offset: 0x1010
Retention: Retained
IsDeepSleep: No
Comment: Clock division control to divide and generate clk_mem from clk_hf0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	INT_DIV	RW	RW	0	Integer division by (1+INT_DIV). Allows for integer divisions in the range [1, 256] (INT_DIV is in the range [0, 255]). Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

5.1.20 CPUSS_CM0_INT0_STATUS

Description: CM0+ interrupt 0 status
Address: 0x40201100
Offset: 0x1100
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 0. Multiple system interrupts can be mapped on the same CPU interrupt. The selected system interrupt is the system interrupt with the lowest system interrupt index that has an activated interrupt request at the time of the fetch (system_interrupts[SYSTEM_INT_IDX] is '1'). The CPU interrupt handler SW can read SYSTEM_INT_IDX to determine the system interrupt that activated the handler.
31	SYSTEM_INT_VALID	R	R	0	Valid indication for SYSTEM_INT_IDX. When '0', no system interrupt for CPU interrupt 0 is valid/activated.

5.1.21 CPUSS_CM0_INT1_STATUS

Description: CM0+ interrupt 1 status
Address: 0x40201104
Offset: 0x1104
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 1. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.22 CPUSS_CM0_INT2_STATUS

Description: CM0+ interrupt 2 status
Address: 0x40201108
Offset: 0x1108
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 2. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.23 CPUSS_CM0_INT3_STATUS

Description: CM0+ interrupt 3 status
Address: 0x4020110C
Offset: 0x110C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 3. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.24 CPUSS_CM0_INT4_STATUS

Description: CM0+ interrupt 4 status
Address: 0x40201110
Offset: 0x1110
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 4. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.25 CPUSS_CM0_INT5_STATUS

Description: CM0+ interrupt 5 status
Address: 0x40201114
Offset: 0x1114
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 5. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.26 CPUSS_CM0_INT6_STATUS

Description: CM0+ interrupt 6 status
Address: 0x40201118
Offset: 0x1118
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 6. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.27 CPUSS_CM0_INT7_STATUS

Description: CM0+ interrupt 7 status
Address: 0x4020111C
Offset: 0x111C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SYSTEM_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	R	R	Undefined	Lowest CM0+ activated system interrupt index for CPU interrupt 7. See description of CM0_INT0_STATUS.
31	SYSTEM_INT_VALID	R	R	0	See description of CM0_INT0_STATUS.

5.1.28 CPUSS_CM0_VECTOR_TABLE_BASE

Description: CM0+ vector table base
Address: 0x40201120
Offset: 0x1120
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR24 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR24 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR24 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:31	ADDR24	RW	RW	0	The default CM0+ vector table base address is 0x0000:0000 (CM0+ VTOR and reset exception handler address after reset). This is the location of the mirror system ROM memory. This register is provided for SW purposes. It 'survives' a CM0+ warm reset cycle (CM0_CTL.ENABLED). Note: the use of the mirror system ROM memory can be disabled using the protection infrastructure (SMPU).

5.1.29 CPUSS_CM0_NMI_CTL

Description: CM0+ NMI control

Address: 0x40201140

Offset: 0x1140

Retention: Retained

IsDeepSleep: No

Comment: Note that multiple (four) CM0_NMI_CTL registers exist, allowing for multiple (four) system interrupts to be connected to the CPU NMI. The four selected system interrupts are logically OR'd into a single CPU NMI input. The NMI handler may need to investigate all selected system interrupt sources to identify the source of CPU NMI.

Default: 0x3FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYSTEM_INT_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SYSTEM_INT_IDX [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SYSTEM_INT_IDX	RW	RW	1023	System interrupt select for CPU NMI. The reset value ('1023') ensures that the CPU NMI is NOT connected to any system interrupt after DeepSleep reset.

5.1.30 CPUSS_CM7_0_PWR_CTL

Description: CM7_0 power control

Address: 0x40201200

Offset: 0x1200

Retention: Retained

IsDeepSleep: No

Comment: This register controls the CM7_0 power state. Please note that this register must not be modified while the CM7_0 is executing; doing so may corrupt/abort pending bus transaction by the CM7_0 and cause unexpected behaviors in the system, including deadlock. The intended usage of this register is by the CM0+ while the CM7_0 is in DeepSleep mode.
Note that CM7 clocks must be running before accessing this register.

Default: 0xFA050000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	0	Power mode.
	OFF			0	Switch CM7_0 off Power off, clock off, isolate, reset and no retain.
	RESET			1	Reset CM7_0 Clock off, no isolated, no retain and reset. Note: The CM7_0 CPU has a AIRCR.SYSRESETREQ register field that allows the CM7_0 to reset the complete device (RESET only resets the CM7_0), resulting in a warm boot.
	RETAINED			2	Put CM7_0 in Retained mode This can only become effective if CM7_0 is in SleepDeep mode. Check PWR_DONE flag to see if CM7_0 RETAINED state has been reached. Power off, clock off, isolate, no reset and retain.
	ENABLED			3	Switch CM7_0 on. Power on, clock on, no isolate, no reset and no retain.
16:31	VECTKEYSTAT	R	R	64005	Register key (to prevent accidental writes). - Should be written with a 0x05fa key value for the write to take effect. - Always reads as 0xfa05. Note: Although the SW attribute for this field says "R", SW need to write the key 0x05fa in this field for this register write to happen. This is a built in protection provided to prevent accidental writes from SW.

5.1.31 CPUSS_CM7_0_PWR_DELAY_CTL

Description: CM7 0 power delay control
Address: 0x40201204
Offset: 0x1204
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x12C

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						UP [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	UP	RW	RW	300	Number clock cycles delay needed after power domain power up

5.1.32 CPUSS_CM7_1_PWR_CTL

Description: CM7 1 power control
Address: 0x40201210
Offset: 0x1210
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0xFA050000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	0	Refer CM7_0_PWR_CTL description.
	OFF			0	Refer CM7_0_PWR_CTL description.
	RESET			1	Refer CM7_0_PWR_CTL description.
	RETAINED			2	Refer CM7_0_PWR_CTL description.
	ENABLED			3	Refer CM7_0_PWR_CTL description.
16:31	VECTKEYSTAT	R	R	64005	Refer CM7_0_PWR_CTL description.

5.1.33 CPUSS_CM7_1_PWR_DELAY_CTL

Description: CM7 1 power delay control
Address: 0x40201214
Offset: 0x1214
Retention: Retained
IsDeepSleep: No
Comment: Note that CM7 clocks must be running before accessing this register.
Default: 0x12C

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						UP [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	UP	RW	RW	300	Number clock cycles delay needed after power domain power up

5.1.34 CPUSS_RAM0_CTL0

Description: RAM 0 control
Address: 0x40201300
Offset: 0x1300
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x30001

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						SLOW_WS [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						FAST_WS [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				ECC_CHECK_DIS [19:19]	ECC_INJ_EN [18:18]	ECC_AUTO_CORRECT [17:17]	ECC_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	SLOW_WS	RW	RW	1	Memory wait states for the slow clock domain ('clk_slow') interface. The number of wait states is expressed in 'clk_mem' clock domain cycles.
8:9	FAST_WS	RW	RW	0	Memory wait states for the fast clock domain ('clk_fast_0/1') interface. The number of wait states is expressed in 'clk_mem' clock domain cycles.
16	ECC_EN	RW	RW	1	Enable ECC checking: '0': Disabled. '1': Enabled.
17	ECC_AUTO_CORRECT	RW	RW	1	HW ECC autocorrect functionality: '0': Disabled. '1': Enabled. HW automatically writes back SRAM with corrected data when a recoverable ECC error is detected.
18	ECC_INJ_EN	RW	RW	0	Enable ECC parity injection. Instead of calculating the parity from the write data to the RAM, the parity is taken from ECC_CTL PARITY upon a match of ECC_CTL WORD_ADDR. The write data can be of any size. This bit is ignored when ECC_EN=0. Note: Parity injection invalidates the write buffer for this word address. If only a part of 64-bit data is written and consistency should be maintained, RAMC#_STATUS WB_EMPTY=1 should be checked before.
19	ECC_CHECK_DIS	RW	RW	0	Disable ECC checking and thus fault reports. This also disables ECC correction (required to enable initialization). Intended usage is initialization. This bit is ignored when ECC_EN=0.

5.1.35 CPUSS_RAM0_STATUS

Description: RAM 0 status
Address: 0x40201304
Offset: 0x1304
Retention: Retained
IsDeepSleep: No
Comment: This register is for the CPUSS system SRAM controller 0.
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WB_EMPTY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WB_EMPTY	R	R	1	Write buffer empty. This information is used when entering DeepSleep power mode: WB_EMPTY must be '1' before a transition to system DeepSleep power mode. '0': Write buffer NOT empty. '1': Write buffer empty. Note: the SRAM controller write buffer is only used when ECC checking is enabled. (RAMi_CTL.ECC_EN is '1').

5.1.36 CPUSS_RAM0_PWR_MACRO_CTL

Description: RAM 0 power control
Address: 0x40201340
Offset: 0x1340
Retention: Retained
IsDeepSleep: No
Comment: These registers control the system SRAM 0 power states of a single macro. System SRAM 0 consists of up to sixteen 32 kB macros. Each macro is a single power partition and is controlled through a dedicated control field in one of these registers.
Default: 0xFA050003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	3	Power mode.
	OFF			0	Turn OFF the SRAM. This will turn OFF both array and periphery power of the SRAM and SRAM memory contents are lost.
	RESERVED			1	undefined
	RETAINED			2	Keep SRAM in Retained mode. This will turn OFF the SRAM periphery power, but array power is ON to retain memory contents.
	ENABLED			3	Enable SRAM for regular operation.
16:31	VECTKEYSTAT	R	R	64005	Register key (to prevent accidental writes). - Should be written with a 0x05fa key value for the write to take effect. - Always reads as 0xfa05. Note: Although the SW attribute for this field says "R", SW need to write the key 0x05fa in this field for this register write to happen. This is a built in protection provided to prevent accidental writes from SW.

5.1.37 CPUSS_RAM1_CTL0

Description: RAM 1 control
Address: 0x40201380
Offset: 0x1380
Retention: Retained
IsDeepSleep: No
Comment: This register is for the CPUSS system SRAM controller 1.
Default: 0x30001

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						SLOW_WS [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						FAST_WS [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				ECC_CHECK_DIS [19:19]	ECC_INJ_EN [18:18]	ECC_AUTO_CORRECT [17:17]	ECC_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	SLOW_WS	RW	RW	1	Refer RAM0_CTL0 description.
8:9	FAST_WS	RW	RW	0	Refer RAM0_CTL0 description.
16	ECC_EN	RW	RW	1	Refer RAM0_CTL0 description.
17	ECC_AUTO_CORRECT	RW	RW	1	Refer RAM0_CTL0 description.
18	ECC_INJ_EN	RW	RW	0	Enable ECC parity injection. Instead of calculating the parity from the write data to the RAM, the parity is taken from ECC_CTL PARITY upon a match of ECC_CTL WORD_ADDR. The write data can be of any size. This bit is ignored when ECC_EN=0. Note: Parity injection invalidates the write buffer for this word address. If only a part of 64-bit data is written and consistency should be maintained, RAMC#_STATUS WB_EMPTY=1 should be checked before.
19	ECC_CHECK_DIS	RW	RW	0	Disable ECC checking and thus fault reports. This also disables ECC correction (required to enable initialization). Intended usage is initialization. This bit is ignored when ECC_EN=0.

5.1.38 CPUSS_RAM1_STATUS

Description: RAM 1 status
Address: 0x40201384
Offset: 0x1384
Retention: Retained
IsDeepSleep: No
Comment: This register is for the CPUSS system SRAM controller 1.
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WB_EMPTY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WB_EMPTY	R	R	1	Refer RAM0_STATUS description.

5.1.39 CPUSS_RAM1_PWR_CTL

Description: RAM 1 power control

Address: 0x40201388

Offset: 0x1388

Retention: Retained

IsDeepSleep: No

Comment: This register controls the system SRAM 1 power states. System SRAM 1 consists of a single power partition.

Default: 0xFA050003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	3	Power mode.
	OFF			0	Refer RAM0_PWR_MACRO_CTL description.
	RESERVED			1	Undefined.
	RETAINED			2	Refer RAM0_PWR_MACRO_CTL description.
	ENABLED			3	Refer RAM0_PWR_MACRO_CTL description.
16:31	VECTKEYSTAT	R	R	64005	Refer RAM0_PWR_MACRO_CTL description.

5.1.40 CPUSS_RAM_PWR_DELAY_CTL

Description: Power up delay used for all SRAM power domains
Address: 0x402013C0
Offset: 0x13C0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x96

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						UP [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	UP	RW	RW	150	Number clock cycles delay needed after power domain power up

5.1.41 CPUSS_ROM_CTL

Description: ROM control
Address: 0x402013C4
Offset: 0x13C4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						SLOW_WS [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						FAST_WS [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	SLOW_WS	RW	RW	1	Memory wait states for the slow clock domain ('clk_slow'). The number of wait states is expressed in 'clk_mem' clock domain cycles. Timing paths to and from the memory have a (fixed) minimum duration that always needs to be considered/met. The 'clk_mem' clock domain frequency determines this field's value such that the timing paths minimum duration is met. ROM_CTL.SLOW_WS = '0' when clk_mem <=100 MHz. ROM_CTL.SLOW_WS = '1' when 100MHz < clk_mem <=200MHz.
8:9	FAST_WS	RW	RW	0	Memory wait states for the fast clock domain ('clk_fast'). The number of wait states is expressed in 'clk_mem' clock domain cycles. ROM_CTL.FAST_WS = '0' when clk_mem <= 200MHz.

5.1.42 CPUSS_ECC_CTL

Description: ECC control
Address: 0x402013C8
Offset: 0x13C8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORD_ADDR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	WORD_ADDR [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	WORD_ADDR [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	PARITY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	WORD_ADDR	RW	RW	0	Specifies the word address where an error will be injected. - On a write transfer to this SRAM address and when the corresponding RAM0/RAM1/RAM2/ITCM/DTCM ECC_INJ_EN bit is '1', the parity (PARITY) is injected. This field needs to be written with the offset address within the memory, divided by the ECC word width in bytes (for RAM0/RAM1/RAM2/ITCM this is 8, for DTCM this is 4). For example, if the RAM0 start address is 0x2800000, and an error is to be injected to address 0x28000080, then this field needs to be configured to 0x000010.
24:31	PARITY	RW	RW	0	ECC parity to use for ECC error injection at address WORD_ADDR. For the DTCM which has only 7 parity bits, PARITY[6:0] is used as ECC parity.

5.1.43 CPUSS_PRODUCT_ID

Description: Product identifier and version (same as CoreSight RomTables)
Address: 0x40201400
Offset: 0x1400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FAMILY_ID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				FAMILY_ID [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	MINOR_REV [23:20]				MAJOR_REV [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:11	FAMILY_ID	R	R	FAMILYID	Family ID. Common ID for a product family.
16:19	MAJOR_REV	R	R	Undefined	Major Revision, starts with 1, increments with all layer tape-out (implemented with metal ECO-able tie-off)
20:23	MINOR_REV	R	R	Undefined	Minor Revision, starts with 1, increments with metal layer only tape-out (implemented with metal ECO-able tie-off)

5.1.44 CPUSS_DP_STATUS

Description: Debug port status
Address: 0x40201410
Offset: 0x1410
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x4

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					SWJ_JTAG_SEL [2:2]	SWJ_DEBUG_EN [1:1]	SWJ_CONNECTED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SWJ_CONNECTED	R	R	0	Specifies if the SWJ debug port is connected; i.e. debug host interface is active: '0': Not connected/not active. '1': Connected/active.
1	SWJ_DEBUG_EN	R	R	0	Specifies if SWJ debug is enabled, i.e. CDBGWRUPACK is '1' and thus debug clocks are on: '0': Disabled. '1': Enabled.
2	SWJ_JTAG_SEL	R	R	1	Specifies if the JTAG or SWD interface is selected. This signal is valid when DP_CTL.PTM_SEL is '0' (SWJ mode selected) and SWJ_CONNECTED is '1' (SWJ is connected). '0': SWD selected. '1': JTAG selected.

5.1.45 CPUSS_AP_CTL

Description: Access port control

Address: 0x40201414

Offset: 0x1414

Retention: Retained

IsDeepSleep: No

Comment: This register enables individual test controller access ports (AP). Note that the system AP is further controlled by a AP specific MPU, the SMPU and PPU. The system AP MPU may be programmed to provide no or limited test controller access capabilities.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					SYS_ENABLE [2:2]	CM7_ENABLE [1:1]	CM0_ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					SYS_DISABLE [18:18]	CM7_DISABLE [17:17]	CM0_DISABLE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CM0_ENABLE	RW	RW	0	Enables the CM0 AP interface: '0': Disabled. '1': Enabled.
1	CM7_ENABLE	RW	RW	0	Enables the CM7_0 and CM7_1 AP interface: '0': Disabled. '1': Enabled.
2	SYS_ENABLE	RW	RW	0	Enables the system AP interface: '0': Disabled. '1': Enabled.
16	CM0_DISABLE	RW1S	RW1S	0	Disables the CM0 AP interface: '0': Enabled. '1': Disabled. Typically, this field is set by the Cypress boot code with information from eFUSE. The access port is only enabled when CM0_DISABLE is '0' and CM0_ENABLE is '1'.
17	CM7_DISABLE	RW1S	RW1S	0	Disables the CM7_0 and CM7_1 AP interface: '0': Enabled. '1': Disabled. Typically, this field is set by the Cypress boot code with information from eFUSE. The access port is only enabled when CM7_DISABLE is '0' and CM7_ENABLE is '1'.

Bits	Name	SW	HW	Default or Enum	Description
18	SYS_DISABLE	RW1S	RW1S	0	Disables the system AP interface: '0': Enabled. '1': Disabled. Typically, this field is set by the Cypress boot code with information from eFUSE. The access port is only enabled when SYS_DISABLE is '0' and SYS_ENABLE is '1'.

5.1.46 CPUSS_BUFF_CTL

Description: Buffer control

Address: 0x40201500

Offset: 0x1500

Retention: Retained

IsDeepSleep: No

Comment: The ARM CM0+ and CM7 CPUs use bufferable write transfers to the peripherals by default. As a result, CPU completion of the write transfer does not guarantee that the write transfer reached its destination, as the transfer may be buffered/posted in the bus infrastructure. Moreover, it is possible that the write transfer does not take place at all due to a PPU violation or a slave error, and in this case the resulting bus error response is not passed to the CPU. This may cause complications if the CPU assumes that completion of the write transfer implies that the write transfer has taken effect in a peripheral (e.g. clearing a peripheral's interrupt cause field). There are multiple possibilities to address this complication:

- Follow the write transfer with a read transfer from the same address, and check that the read data matches the expectation.
- Configure a fault structure such that the following faults are reported: MS_PPU_0 to MS_PPU_4 to report PPU violations, timeout or bus errors in the PERI master interfaces, and GROUP_FAULT_0 to GROUP_FAULT_15 (only for the existing peripheral groups) to report decode or slave errors in the peripheral groups. The CPU can perform a read transfer after a series of write transfers to the same peripheral group. If the read transfer completes and no faults are reported, then the write transfers have been executed. Note that the fault reporting has some latency, so the faults may be reported after the completion of the read transfer.
- Use the CPU MPU to set write transfers to non-bufferable/non-posted.
- Use BUFF_CTL.WRITE_BUFF to ensure that all write transfers are non-bufferable/non-posted.

Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WRITE_BUFF [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WRITE_BUFF	RW	RW	1	Specifies if write transfer can be buffered in the bus infrastructure bridges: '0': Write transfers are not buffered, independent of the transfer's bufferable attribute. '1': Write transfers can be buffered, if the transfer's bufferable attribute indicates that the transfer is a bufferable/posted write.

5.1.47 CPUSS_SYSTICK_CTL

Description: SysTick timer control

Address: 0x40201600

Offset: 0x1600

Retention: Retained

IsDeepSleep: No

Comment: The CPUSS SYSTICK_CTL MMIO NOREF, SKEW, TENMS register fields are reflected in the CPU's SysTick timer calibration register: SYST_CALIB (the CLOCK_SOURCE field is NOT reflected and only SW accessible through the CPUSS SYSTICK_CTL MMIO register).

Default: 0x40000147

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TENMS [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TENMS [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TENMS [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	NOREF [31:31]	SKEW [30:30]	None [29:26]				CLOCK_SOURCE [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	TENMS	RW	RW	327	Specifies the number of clock source cycles (minus 1) that make up 10 ms. E.g., for a 32,768 Hz reference clock, TENMS is 328 - 1 = 327.
24:25	CLOCK_SOURCE	RW	RW	0	Specifies an external clock source: '0': The low frequency clock 'clk_lf' is selected. The precision of this clock depends on whether the low frequency clock source is a SRSS internal RC oscillator (imprecise) or a device external crystal oscillator (precise). '1': The internal main oscillator (IMO) clock 'clk_imo' is selected. The MXS40 platform uses a fixed frequency IMO clock. o '2': The external crystal oscillator (ECO) clock 'clk_eco' is selected. '3': The SRSS 'clk_timer' is selected ('clk_timer' is a divided/gated version of 'clk_hf' or 'clk_imo'). Note: If NOREF is '1', the CLOCK_SOURCE value is NOT used. Note: It is SW's responsibility to provide the correct NOREF, SKEW and TENMS field values for the selected clock source.
30	SKEW	RW	RW	1	Specifies the precision of the clock source and if the TENMS field represents exactly 10 ms (clock source frequency is a multiple of 100 Hz). This affects the suitability of the SysTick timer as a SW real-time clock: '0': Precise. '1': Imprecise.
31	NOREF	RW	RW	0	Specifies if an external clock source is provided: '0': An external clock source is provided. '1': An external clock source is NOT provided and only the CPU internal clock can be used as SysTick timer clock source.

5.1.48 CPUSS_CAL_SUP_SET

Description: Calibration support set and read
Address: 0x40201800
Offset: 0x1800
Retention: Retained
IsDeepSleep: No
Comment: For ETAS support
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW1S	RW1S	0	Read without side effect, write 1 to set

5.1.49 CPUSS_CAL_SUP_CLR

Description: Calibration support clear and reset
Address: 0x40201804
Offset: 0x1804
Retention: Retained
IsDeepSleep: No
Comment: Read side effect: reset on read (even when read from debug host)
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW1C	RW1C	0	Read side effect: when read all bits are cleared, write 1 to clear a specific bit Note: no exception for the debug host, it also causes the read side effect

5.1.50 CPUSS_CM0_PC_CTL

Description: CM0+ protection context control
Address: 0x40202000
Offset: 0x2000
Retention: Retained
IsDeepSleep: No
Comment: The CM0_PC_CTL and CM0_Pci_HANDLER register are typically initialized by the boot code.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				VALID [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	VALID	RW	RW	0	Valid fields for the protection context handler CM0_Pci_HANDLER registers: Bit 0: Valid field for CM0_PC0_HANDLER. Bit 1: Valid field for CM0_PC1_HANDLER. Bit 2: Valid field for CM0_PC2_HANDLER. Bit 3: Valid field for CM0_PC3_HANDLER.

5.1.51 CPUSS_CM0_PC0_HANDLER

Description: CM0+ protection context 0 handler
Address: 0x40202040
Offset: 0x2040
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	RW	RW	0	Address of the protection context 0 handler. This field is used to detect entry to Cypress 'trusted' code through an exception/interrupt.

5.1.52 CPUSS_CM0_PC1_HANDLER

Description: CM0+ protection context 1 handler
Address: 0x40202044
Offset: 0x2044
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	RW	RW	0	Address of the protection context 1 handler.

5.1.53 CPUSS_CM0_PC2_HANDLER

Description: CM0+ protection context 2 handler
Address: 0x40202048
Offset: 0x2048
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	RW	RW	0	Address of the protection context 2 handler.

5.1.54 CPUSS_CM0_PC3_HANDLER

Description: CM0+ protection context 3 handler
Address: 0x4020204C
Offset: 0x204C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	RW	RW	0	Address of the protection context 3 handler.

5.1.55 CPUSS_PROTECTION

Description: Protection status
Address: 0x402020C4
Offset: 0x20C4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					STATE [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	STATE	RW	RW	0	Protection state: '0': UNKNOWN. '1': VIRGIN. '2': NORMAL. '3': SECURE. '4': DEAD. The following state transistions are allowed (and enforced by HW): - UNKNOWN => VIRGIN/NORMAL/SECURE/DEAD - NORMAL => DEAD - SECURE => DEAD An attempt to make a NOT allowed state transition will NOT affect this register field.
	UNKNOWN			0	N/A
	VIRGIN			1	N/A
	NORMAL			2	N/A
	SECURE			3	N/A
	DEAD			4	N/A

5.1.56 CPUSS_TRIM_ROM_CTL

Description: ROM trim control

Address: 0x40202100

Offset: 0x2100

Retention: Retained

IsDeepSleep: No

Comment: This register is used to trim ALL ROM memories in the device. Different operating Voltages may require different trim settings.

SW should change the TRIM settings appropriately while changing the core operating voltage (E.g while switching from 1.1v to 0.9v or vice versa on a ULP device).

Refer respective ROM IP BROS for the trim settings required based on operating voltage.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIM [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TRIM [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TRIM [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	TRIM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TRIM	RW	RW	ROM_TRIM_DEFAULT	For ARM ROMs the bits are defined as follows [2:0] EMA: Extra Margin Adjustment (0 is the fastest setting) Recommended default value: EMA=2 (ROM_TRIM_DEFAULT=0x0000_0002, ROM_TRIM_WIDTH=3) For Synopsys ROMs the bits are defined as follows: [3:0] RM: Read-Write margin control. This is used for setting the Read-Write margin. It programs the sense amplifier differential setting and allows the trade off between speed and robustness. - RM[1:0] values control access time and cycle time of the memory. RM[1:0] = '0' is the slowest possible mode of operation for the memory. This setting is required for VDDMIN operation. - RM[3:2] are factory pins reserved for debug mode and should be set to '0'. [4] RME: Read-Write margin enable control. This selects between the default Read-Write margin setting, and the external pin Read-Write margin setting. Recommended default value for LP: RME=1, RM=2 (ROM_TRIM_DEFAULT=0x0000_0012, ROM_TRIM_WIDTH=5) Recommended default value for ULP: RME=1, RM=3 (ROM_TRIM_DEFAULT=0x0000_0013, ROM_TRIM_WIDTH=5)

5.1.57 CPUSS_TRIM_RAM_CTL

Description: RAM trim control for less than 100MHz SRAMs

Address: 0x40202104

Offset: 0x2104

Retention: Retained

IsDeepSleep: No

Comment: This register is used to trim SRAM memories clocked at 100MHz or less in the device. Different operating Voltages may require different trim settings. SW should change the TRIM settings appropriately while changing the core operating voltage (E.g while switching from 1.1v to 0.9v or vice versa on a ULP device). Refer respective SRAM IP BROS for the trim settings required based on operating voltage.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TRIM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TRIM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TRIM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TRIM	RW	RW	RAM_TRIM_DEFAULT	For ARM RAMs the bits are defined as follows [2:0] EMA: Extra Margin Adjustment (0 is the fastest setting) [4:3] EMAW: Extra Margin Adjustment for Writes (0 is the fastest setting) [7:5] CTL_BIAS: Control the SRAM retention mode back bias control circuit in the SRAM power switches that implement bias control: 0=no back bias; 1=max back bias, 7=min back bias' Recommended default value: CTL_BIAS=3, EMAW=0, EMA=2 (RAM_TRIM_DEFAULT=0x0000_0062, RAM_TRIM_WIDTH=8) Note: DW0, DW1 SRAMs uses bias control power switches. For Synopsys RAMs the bits are defined as follows: [3:0] Read-Write margin control. This is used for setting the Read-Write margin. It programs the sense amplifier differential setting and allows the trade off between speed and robustness. - RM[1:0] values control access time and cycle time of the memory. RM[1:0] = '0' is the slowest possible mode of operation for the memory. This setting is required for VDDMIN operation. - RM[3:2] are factory pins reserved for debug mode and should be set to '0'. [4] RME: Read-Write margin enable control. This selects between the default Read-Write margin setting, and the external RM[3:0] Read-Write margin setting. [7:5] WPULSE: Write Assist Pulse to control pulse width of negative voltage on SRAM bitline. [9:8] RA: Read Assist control for WL under-drive. [14:12] WA: Write assist enable control (Active High). - WA[2:0] Write Assist pins to control negative voltage on SRAM bitline. Recommended default value for LP: WA=4, RA=0, WPULSE=0, RME=1, RM=3 (RAM_TRIM_DEFAULT=0x0000_4013, RAM_TRIM_WIDTH=15) Recommended default value for ULP: WA=6, RA=0, WPULSE=0, RME=1, RM=2 (RAM_TRIM_DEFAULT=0x0000_6012, RAM_TRIM_WIDTH=15)

5.1.58 CPUSS_TRIM_RAM200_CTL

Description: RAM trim control for 100MHz - 200MHz SRAMs
Address: 0x40202108
Offset: 0x2108
Retention: Retained
IsDeepSleep: No
Comment: See TRIM_RAM_CTL
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TRIM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TRIM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TRIM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TRIM	RW	RW	RAM_TRIM_DEFAULT	See TRIM_RAM_CTL for description. System SRAM memories (SRAM0,1,2) are connected to this register. System SRAM0 uses bias control power switch,so bits [7:5] of this register controls the bias pins of the SRAM0 power switch.

5.1.59 CPUSS_TRIM_RAM350_CTL

Description: RAM trim control for more than 200MHz SRAMs
Address: 0x4020210C
Offset: 0x210C
Retention: Retained
IsDeepSleep: No
Comment: See TRIM_RAM_CTL
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TRIM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TRIM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TRIM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TRIM	RW	RW	RAM_TRIM_DEFAULT	See TRIM_RAM_CTL for description. CM7 Cache and TCM memories are connected to this register. All CM7 cache and TCM SRAM macros are controlled using bias control power switches, so bits [7:5] of this register controls the bias pins of the CM7 cache and TCM SRAM power switches.

5.1.60 CPUSS_CM0_SYSTEM_INT_CTL

Description: CM0+ system interrupt control
Address: 0x40208000
Offset: 0x8000
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CM0_CPU_INT_IDX [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CPU_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	CM0_CPU_INT_IDX	RW	RW	Undefined	CPU interrupt index (legal range [0, 7]). This field specifies to which CPU interrupt the system interrupt is mapped. E.g., if CPU_INT_IDX is '6', the system interrupt is mapped to CPU interrupt '6'. Note: it is possible to map multiple system interrupts to the same CPU interrupt. It is advised to assign different priorities to the CPU interrupts and to assign system interrupts to CPU interrupts accordingly.
31	CPU_INT_VALID	RW	RW	0	Interrupt enable: '0': Disabled. The system interrupt will NOT be mapped to any CPU interrupt. '1': Enabled. The system interrupt is mapped on CPU interrupt CPU_INT_IDX. Note: the CPUs have dedicated XXX_SYSTEM_INT_CTL registers. In other words, the CPUs can use different CPU interrupts for the same system interrupt. However, typically only one of the CPUs will have the ENABLED field of a specific system interrupt set to '1'.

5.1.61 CPUSS_CM7_0_SYSTEM_INT_CTL

Description: CM7 0 system interrupt control
Address: 0x4020A000
Offset: 0xA000
Retention: Retained
IsDeepSleep: No
Comment: Only present when SYSTEM_IRQ_PRESENT is '1'
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CPU_INT_IDX [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CPU_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CPU_INT_IDX	RW	RW	Undefined	CPU interrupt index (legal range [0, 15]). This field specifies to which CPU interrupt the system interrupt is mapped. E.g., if CPU_INT_IDX is '6', the system interrupt is mapped to CPU interrupt '6'. Note: it is possible to map multiple system interrupts to the same CPU interrupt. It is advised to assign different priorities to the CPU interrupts and to assign system interrupts to CPU interrupts accordingly.
31	CPU_INT_VALID	RW	RW	0	Interrupt enable: '0': Disabled. The system interrupt will NOT be mapped to any CPU interrupt. '1': Enabled. The system interrupt is mapped on CPU interrupt CPU_INT_IDX. Note: the CPUs have dedicated XXX_SYSTEM_INT_CTL registers. In other words, the CPUs can use different CPU interrupts for the same system interrupt. However, typically only one of the CPUs will have the ENABLED field of a specific system interrupt set to '1'.

5.1.62 CPUSS_CM7_1_SYSTEM_INT_CTL

Description: CM7 1 system interrupt control
Address: 0x4020C000
Offset: 0xC000
Retention: Retained
IsDeepSleep: No
Comment: Only present when SYSTEM_IRQ_PRESENT is '1' and CM7_1_PRESENT is '1'
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				CPU_INT_IDX [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CPU_INT_VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CPU_INT_IDX	RW	RW	Undefined	Refer CM7_0_SYSTEM_INT_CTL description.
31	CPU_INT_VALID	RW	RW	0	Refer CM7_0_SYSTEM_INT_CTL description.

6 CRYPTO

Description Cryptography component
Base Address 0x40100000
Size 0x10000
Slave Num MMIO1 - 0

Register Name	Address	Permission	Description
CRYPTO_CTL	0x40100000	FULL	Control
CRYPTO_RAM_PWR_CTL	0x40100008	FULL	SRAM power control
CRYPTO_RAM_PWR_DELAY_CTL	0x4010000C	FULL	SRAM power delay control
CRYPTO_ECC_CTL	0x40100010	FULL	ECC control
CRYPTO_ERROR_STATUS0	0x40100020	FULL	Error status 0
CRYPTO_ERROR_STATUS1	0x40100024	FULL	Error status 1
CRYPTO_INTR	0x40100100	FULL	Interrupt register
CRYPTO_INTR_SET	0x40100104	FULL	Interrupt set register
CRYPTO_INTR_MASK	0x40100108	FULL	Interrupt mask register
CRYPTO_INTR_MASKED	0x4010010C	FULL	Interrupt masked register
CRYPTO_PR_LFSR_CTL0	0x40100200	FULL	Pseudo random LFSR control 0
CRYPTO_PR_LFSR_CTL1	0x40100204	FULL	Pseudo random LFSR control 1
CRYPTO_PR_LFSR_CTL2	0x40100208	FULL	Pseudo random LFSR control 2
CRYPTO_PR_MAX_CTL	0x4010020C	FULL	Pseudo random maximum control
CRYPTO_PR_CMD	0x40100210	FULL	Pseudo random command
CRYPTO_PR_RESULT	0x40100218	FULL	Pseudo random result
CRYPTO_TR_CTL0	0x40100280	FULL	True random control 0
CRYPTO_TR_CTL1	0x40100284	FULL	True random control 1
CRYPTO_TR_CTL2	0x40100288	FULL	True random control 2
CRYPTO_TR_STATUS	0x4010028C	FULL	True random status
CRYPTO_TR_CMD	0x40100290	FULL	True random command
CRYPTO_TR_RESULT	0x40100298	FULL	True random result
CRYPTO_TR_GARO_CTL	0x401002A0	FULL	True random GARO control
CRYPTO_TR_FIRO_CTL	0x401002A4	FULL	True random FIRO control
CRYPTO_TR_MON_CTL	0x401002C0	FULL	True random monitor control
CRYPTO_TR_MON_CMD	0x401002C8	FULL	True random monitor command
CRYPTO_TR_MON_RC_CTL	0x401002D0	FULL	True random monitor RC control
CRYPTO_TR_MON_RC_STATUS0	0x401002D8	FULL	True random monitor RC status 0
CRYPTO_TR_MON_RC_STATUS1	0x401002DC	FULL	True random monitor RC status 1
CRYPTO_TR_MON_AP_CTL	0x401002E0	FULL	True random monitor AP control
CRYPTO_TR_MON_AP_STATUS0	0x401002E8	FULL	True random monitor AP status 0
CRYPTO_TR_MON_AP_STATUS1	0x401002EC	FULL	True random monitor AP status 1
CRYPTO_STATUS	0x40101004	FULL	Status
CRYPTO_INSTR_FF_CTL	0x40101040	FULL	Instruction FIFO control
CRYPTO_INSTR_FF_STATUS	0x40101044	FULL	Instruction FIFO status
CRYPTO_INSTR_FF_WR	0x40101048	FULL	Instruction FIFO write
CRYPTO_LOAD0_FF_STATUS	0x401010C0	FULL	Load 0 FIFO status
CRYPTO_LOAD1_FF_STATUS	0x401010D0	FULL	Load 1 FIFO status
CRYPTO_STORE_FF_STATUS	0x401010F0	FULL	Store FIFO status
CRYPTO_AES_CTL	0x40101100	FULL	AES control
CRYPTO_RESULT	0x40101180	FULL	Result
CRYPTO_CRC_CTL	0x40101400	FULL	CRC control
CRYPTO_CRC_DATA_CTL	0x40101410	FULL	CRC data control
CRYPTO_CRC_POL_CTL	0x40101420	FULL	CRC polynomial control
CRYPTO_CRC_REM_CTL	0x40101440	FULL	CRC remainder control
CRYPTO_CRC_REM_RESULT	0x40101448	FULL	CRC remainder result
CRYPTO_VU_CTL0	0x40101480	FULL	Vector unit control 0
CRYPTO_VU_CTL1	0x40101484	FULL	Vector unit control 1
CRYPTO_VU_CTL2	0x40101488	FULL	Vector unit control 2
CRYPTO_VU_STATUS	0x40101490	FULL	Vector unit status
CRYPTO_VU_RF_DATA0	0x401014C0	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA1	0x401014C4	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA2	0x401014C8	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA3	0x401014CC	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA4	0x401014D0	FULL	Vector unit register-file

Register Name	Address	Permission	Description
CRYPTO_VU_RF_DATA5	0x401014D4	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA6	0x401014D8	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA7	0x401014DC	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA8	0x401014E0	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA9	0x401014E4	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA10	0x401014E8	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA11	0x401014EC	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA12	0x401014F0	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA13	0x401014F4	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA14	0x401014F8	FULL	Vector unit register-file
CRYPTO_VU_RF_DATA15	0x401014FC	FULL	Vector unit register-file
CRYPTO_DEV_KEY_ADDR0_CTL	0x40102000	READ	Device key address 0 control
CRYPTO_DEV_KEY_ADDR0	0x40102004	READ	Device key address 0
CRYPTO_DEV_KEY_ADDR1_CTL	0x40102020	READ	Device key address 1 control
CRYPTO_DEV_KEY_ADDR1	0x40102024	READ	Device key address 1 control
CRYPTO_DEV_KEY_STATUS	0x40102080	READ	Device key status
CRYPTO_DEV_KEY_CTL0	0x40102100	FULL	Device key control 0
CRYPTO_DEV_KEY_CTL1	0x40102120	FULL	Device key control 1
CRYPTO_MEM_BUFF0	0x40108000	FULL	Memory buffer
CRYPTO_MEM_BUFF1	0x40108004	FULL	Memory buffer
CRYPTO_MEM_BUFF2	0x40108008	FULL	Memory buffer
CRYPTO_MEM_BUFF3	0x4010800C	FULL	Memory buffer
CRYPTO_MEM_BUFF4	0x40108010	FULL	Memory buffer
CRYPTO_MEM_BUFF5	0x40108014	FULL	Memory buffer
CRYPTO_MEM_BUFF6	0x40108018	FULL	Memory buffer
CRYPTO_MEM_BUFF7	0x4010801C	FULL	Memory buffer
CRYPTO_MEM_BUFF8	0x40108020	FULL	Memory buffer
CRYPTO_MEM_BUFF9	0x40108024	FULL	Memory buffer
CRYPTO_MEM_BUFF10	0x40108028	FULL	Memory buffer
CRYPTO_MEM_BUFF11	0x4010802C	FULL	Memory buffer
CRYPTO_MEM_BUFF12	0x40108030	FULL	Memory buffer
CRYPTO_MEM_BUFF13	0x40108034	FULL	Memory buffer
CRYPTO_MEM_BUFF14	0x40108038	FULL	Memory buffer
CRYPTO_MEM_BUFF15	0x4010803C	FULL	Memory buffer
CRYPTO_MEM_BUFF16	0x40108040	FULL	Memory buffer
CRYPTO_MEM_BUFF17	0x40108044	FULL	Memory buffer
CRYPTO_MEM_BUFF18	0x40108048	FULL	Memory buffer
CRYPTO_MEM_BUFF19	0x4010804C	FULL	Memory buffer
CRYPTO_MEM_BUFF20	0x40108050	FULL	Memory buffer
CRYPTO_MEM_BUFF21	0x40108054	FULL	Memory buffer
CRYPTO_MEM_BUFF22	0x40108058	FULL	Memory buffer
CRYPTO_MEM_BUFF23	0x4010805C	FULL	Memory buffer
CRYPTO_MEM_BUFF24	0x40108060	FULL	Memory buffer
CRYPTO_MEM_BUFF25	0x40108064	FULL	Memory buffer
CRYPTO_MEM_BUFF26	0x40108068	FULL	Memory buffer
CRYPTO_MEM_BUFF27	0x4010806C	FULL	Memory buffer
CRYPTO_MEM_BUFF28	0x40108070	FULL	Memory buffer
CRYPTO_MEM_BUFF29	0x40108074	FULL	Memory buffer
CRYPTO_MEM_BUFF30	0x40108078	FULL	Memory buffer
CRYPTO_MEM_BUFF31	0x4010807C	FULL	Memory buffer
CRYPTO_MEM_BUFF32	0x40108080	FULL	Memory buffer
CRYPTO_MEM_BUFF33	0x40108084	FULL	Memory buffer
CRYPTO_MEM_BUFF34	0x40108088	FULL	Memory buffer
CRYPTO_MEM_BUFF35	0x4010808C	FULL	Memory buffer
CRYPTO_MEM_BUFF36	0x40108090	FULL	Memory buffer
CRYPTO_MEM_BUFF37	0x40108094	FULL	Memory buffer
CRYPTO_MEM_BUFF38	0x40108098	FULL	Memory buffer
CRYPTO_MEM_BUFF39	0x4010809C	FULL	Memory buffer
CRYPTO_MEM_BUFF40	0x401080A0	FULL	Memory buffer
CRYPTO_MEM_BUFF41	0x401080A4	FULL	Memory buffer
CRYPTO_MEM_BUFF42	0x401080A8	FULL	Memory buffer
CRYPTO_MEM_BUFF43	0x401080AC	FULL	Memory buffer
CRYPTO_MEM_BUFF44	0x401080B0	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF45	0x401080B4	FULL	Memory buffer
CRYPTO_MEM_BUFF46	0x401080B8	FULL	Memory buffer
CRYPTO_MEM_BUFF47	0x401080BC	FULL	Memory buffer
CRYPTO_MEM_BUFF48	0x401080C0	FULL	Memory buffer
CRYPTO_MEM_BUFF49	0x401080C4	FULL	Memory buffer
CRYPTO_MEM_BUFF50	0x401080C8	FULL	Memory buffer
CRYPTO_MEM_BUFF51	0x401080CC	FULL	Memory buffer
CRYPTO_MEM_BUFF52	0x401080D0	FULL	Memory buffer
CRYPTO_MEM_BUFF53	0x401080D4	FULL	Memory buffer
CRYPTO_MEM_BUFF54	0x401080D8	FULL	Memory buffer
CRYPTO_MEM_BUFF55	0x401080DC	FULL	Memory buffer
CRYPTO_MEM_BUFF56	0x401080E0	FULL	Memory buffer
CRYPTO_MEM_BUFF57	0x401080E4	FULL	Memory buffer
CRYPTO_MEM_BUFF58	0x401080E8	FULL	Memory buffer
CRYPTO_MEM_BUFF59	0x401080EC	FULL	Memory buffer
CRYPTO_MEM_BUFF60	0x401080F0	FULL	Memory buffer
CRYPTO_MEM_BUFF61	0x401080F4	FULL	Memory buffer
CRYPTO_MEM_BUFF62	0x401080F8	FULL	Memory buffer
CRYPTO_MEM_BUFF63	0x401080FC	FULL	Memory buffer
CRYPTO_MEM_BUFF64	0x40108100	FULL	Memory buffer
CRYPTO_MEM_BUFF65	0x40108104	FULL	Memory buffer
CRYPTO_MEM_BUFF66	0x40108108	FULL	Memory buffer
CRYPTO_MEM_BUFF67	0x4010810C	FULL	Memory buffer
CRYPTO_MEM_BUFF68	0x40108110	FULL	Memory buffer
CRYPTO_MEM_BUFF69	0x40108114	FULL	Memory buffer
CRYPTO_MEM_BUFF70	0x40108118	FULL	Memory buffer
CRYPTO_MEM_BUFF71	0x4010811C	FULL	Memory buffer
CRYPTO_MEM_BUFF72	0x40108120	FULL	Memory buffer
CRYPTO_MEM_BUFF73	0x40108124	FULL	Memory buffer
CRYPTO_MEM_BUFF74	0x40108128	FULL	Memory buffer
CRYPTO_MEM_BUFF75	0x4010812C	FULL	Memory buffer
CRYPTO_MEM_BUFF76	0x40108130	FULL	Memory buffer
CRYPTO_MEM_BUFF77	0x40108134	FULL	Memory buffer
CRYPTO_MEM_BUFF78	0x40108138	FULL	Memory buffer
CRYPTO_MEM_BUFF79	0x4010813C	FULL	Memory buffer
CRYPTO_MEM_BUFF80	0x40108140	FULL	Memory buffer
CRYPTO_MEM_BUFF81	0x40108144	FULL	Memory buffer
CRYPTO_MEM_BUFF82	0x40108148	FULL	Memory buffer
CRYPTO_MEM_BUFF83	0x4010814C	FULL	Memory buffer
CRYPTO_MEM_BUFF84	0x40108150	FULL	Memory buffer
CRYPTO_MEM_BUFF85	0x40108154	FULL	Memory buffer
CRYPTO_MEM_BUFF86	0x40108158	FULL	Memory buffer
CRYPTO_MEM_BUFF87	0x4010815C	FULL	Memory buffer
CRYPTO_MEM_BUFF88	0x40108160	FULL	Memory buffer
CRYPTO_MEM_BUFF89	0x40108164	FULL	Memory buffer
CRYPTO_MEM_BUFF90	0x40108168	FULL	Memory buffer
CRYPTO_MEM_BUFF91	0x4010816C	FULL	Memory buffer
CRYPTO_MEM_BUFF92	0x40108170	FULL	Memory buffer
CRYPTO_MEM_BUFF93	0x40108174	FULL	Memory buffer
CRYPTO_MEM_BUFF94	0x40108178	FULL	Memory buffer
CRYPTO_MEM_BUFF95	0x4010817C	FULL	Memory buffer
CRYPTO_MEM_BUFF96	0x40108180	FULL	Memory buffer
CRYPTO_MEM_BUFF97	0x40108184	FULL	Memory buffer
CRYPTO_MEM_BUFF98	0x40108188	FULL	Memory buffer
CRYPTO_MEM_BUFF99	0x4010818C	FULL	Memory buffer
CRYPTO_MEM_BUFF100	0x40108190	FULL	Memory buffer
CRYPTO_MEM_BUFF101	0x40108194	FULL	Memory buffer
CRYPTO_MEM_BUFF102	0x40108198	FULL	Memory buffer
CRYPTO_MEM_BUFF103	0x4010819C	FULL	Memory buffer
CRYPTO_MEM_BUFF104	0x401081A0	FULL	Memory buffer
CRYPTO_MEM_BUFF105	0x401081A4	FULL	Memory buffer
CRYPTO_MEM_BUFF106	0x401081A8	FULL	Memory buffer
CRYPTO_MEM_BUFF107	0x401081AC	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF108	0x401081B0	FULL	Memory buffer
CRYPTO_MEM_BUFF109	0x401081B4	FULL	Memory buffer
CRYPTO_MEM_BUFF110	0x401081B8	FULL	Memory buffer
CRYPTO_MEM_BUFF111	0x401081BC	FULL	Memory buffer
CRYPTO_MEM_BUFF112	0x401081C0	FULL	Memory buffer
CRYPTO_MEM_BUFF113	0x401081C4	FULL	Memory buffer
CRYPTO_MEM_BUFF114	0x401081C8	FULL	Memory buffer
CRYPTO_MEM_BUFF115	0x401081CC	FULL	Memory buffer
CRYPTO_MEM_BUFF116	0x401081D0	FULL	Memory buffer
CRYPTO_MEM_BUFF117	0x401081D4	FULL	Memory buffer
CRYPTO_MEM_BUFF118	0x401081D8	FULL	Memory buffer
CRYPTO_MEM_BUFF119	0x401081DC	FULL	Memory buffer
CRYPTO_MEM_BUFF120	0x401081E0	FULL	Memory buffer
CRYPTO_MEM_BUFF121	0x401081E4	FULL	Memory buffer
CRYPTO_MEM_BUFF122	0x401081E8	FULL	Memory buffer
CRYPTO_MEM_BUFF123	0x401081EC	FULL	Memory buffer
CRYPTO_MEM_BUFF124	0x401081F0	FULL	Memory buffer
CRYPTO_MEM_BUFF125	0x401081F4	FULL	Memory buffer
CRYPTO_MEM_BUFF126	0x401081F8	FULL	Memory buffer
CRYPTO_MEM_BUFF127	0x401081FC	FULL	Memory buffer
CRYPTO_MEM_BUFF128	0x40108200	FULL	Memory buffer
CRYPTO_MEM_BUFF129	0x40108204	FULL	Memory buffer
CRYPTO_MEM_BUFF130	0x40108208	FULL	Memory buffer
CRYPTO_MEM_BUFF131	0x4010820C	FULL	Memory buffer
CRYPTO_MEM_BUFF132	0x40108210	FULL	Memory buffer
CRYPTO_MEM_BUFF133	0x40108214	FULL	Memory buffer
CRYPTO_MEM_BUFF134	0x40108218	FULL	Memory buffer
CRYPTO_MEM_BUFF135	0x4010821C	FULL	Memory buffer
CRYPTO_MEM_BUFF136	0x40108220	FULL	Memory buffer
CRYPTO_MEM_BUFF137	0x40108224	FULL	Memory buffer
CRYPTO_MEM_BUFF138	0x40108228	FULL	Memory buffer
CRYPTO_MEM_BUFF139	0x4010822C	FULL	Memory buffer
CRYPTO_MEM_BUFF140	0x40108230	FULL	Memory buffer
CRYPTO_MEM_BUFF141	0x40108234	FULL	Memory buffer
CRYPTO_MEM_BUFF142	0x40108238	FULL	Memory buffer
CRYPTO_MEM_BUFF143	0x4010823C	FULL	Memory buffer
CRYPTO_MEM_BUFF144	0x40108240	FULL	Memory buffer
CRYPTO_MEM_BUFF145	0x40108244	FULL	Memory buffer
CRYPTO_MEM_BUFF146	0x40108248	FULL	Memory buffer
CRYPTO_MEM_BUFF147	0x4010824C	FULL	Memory buffer
CRYPTO_MEM_BUFF148	0x40108250	FULL	Memory buffer
CRYPTO_MEM_BUFF149	0x40108254	FULL	Memory buffer
CRYPTO_MEM_BUFF150	0x40108258	FULL	Memory buffer
CRYPTO_MEM_BUFF151	0x4010825C	FULL	Memory buffer
CRYPTO_MEM_BUFF152	0x40108260	FULL	Memory buffer
CRYPTO_MEM_BUFF153	0x40108264	FULL	Memory buffer
CRYPTO_MEM_BUFF154	0x40108268	FULL	Memory buffer
CRYPTO_MEM_BUFF155	0x4010826C	FULL	Memory buffer
CRYPTO_MEM_BUFF156	0x40108270	FULL	Memory buffer
CRYPTO_MEM_BUFF157	0x40108274	FULL	Memory buffer
CRYPTO_MEM_BUFF158	0x40108278	FULL	Memory buffer
CRYPTO_MEM_BUFF159	0x4010827C	FULL	Memory buffer
CRYPTO_MEM_BUFF160	0x40108280	FULL	Memory buffer
CRYPTO_MEM_BUFF161	0x40108284	FULL	Memory buffer
CRYPTO_MEM_BUFF162	0x40108288	FULL	Memory buffer
CRYPTO_MEM_BUFF163	0x4010828C	FULL	Memory buffer
CRYPTO_MEM_BUFF164	0x40108290	FULL	Memory buffer
CRYPTO_MEM_BUFF165	0x40108294	FULL	Memory buffer
CRYPTO_MEM_BUFF166	0x40108298	FULL	Memory buffer
CRYPTO_MEM_BUFF167	0x4010829C	FULL	Memory buffer
CRYPTO_MEM_BUFF168	0x401082A0	FULL	Memory buffer
CRYPTO_MEM_BUFF169	0x401082A4	FULL	Memory buffer
CRYPTO_MEM_BUFF170	0x401082A8	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF171	0x401082AC	FULL	Memory buffer
CRYPTO_MEM_BUFF172	0x401082B0	FULL	Memory buffer
CRYPTO_MEM_BUFF173	0x401082B4	FULL	Memory buffer
CRYPTO_MEM_BUFF174	0x401082B8	FULL	Memory buffer
CRYPTO_MEM_BUFF175	0x401082BC	FULL	Memory buffer
CRYPTO_MEM_BUFF176	0x401082C0	FULL	Memory buffer
CRYPTO_MEM_BUFF177	0x401082C4	FULL	Memory buffer
CRYPTO_MEM_BUFF178	0x401082C8	FULL	Memory buffer
CRYPTO_MEM_BUFF179	0x401082CC	FULL	Memory buffer
CRYPTO_MEM_BUFF180	0x401082D0	FULL	Memory buffer
CRYPTO_MEM_BUFF181	0x401082D4	FULL	Memory buffer
CRYPTO_MEM_BUFF182	0x401082D8	FULL	Memory buffer
CRYPTO_MEM_BUFF183	0x401082DC	FULL	Memory buffer
CRYPTO_MEM_BUFF184	0x401082E0	FULL	Memory buffer
CRYPTO_MEM_BUFF185	0x401082E4	FULL	Memory buffer
CRYPTO_MEM_BUFF186	0x401082E8	FULL	Memory buffer
CRYPTO_MEM_BUFF187	0x401082EC	FULL	Memory buffer
CRYPTO_MEM_BUFF188	0x401082F0	FULL	Memory buffer
CRYPTO_MEM_BUFF189	0x401082F4	FULL	Memory buffer
CRYPTO_MEM_BUFF190	0x401082F8	FULL	Memory buffer
CRYPTO_MEM_BUFF191	0x401082FC	FULL	Memory buffer
CRYPTO_MEM_BUFF192	0x40108300	FULL	Memory buffer
CRYPTO_MEM_BUFF193	0x40108304	FULL	Memory buffer
CRYPTO_MEM_BUFF194	0x40108308	FULL	Memory buffer
CRYPTO_MEM_BUFF195	0x4010830C	FULL	Memory buffer
CRYPTO_MEM_BUFF196	0x40108310	FULL	Memory buffer
CRYPTO_MEM_BUFF197	0x40108314	FULL	Memory buffer
CRYPTO_MEM_BUFF198	0x40108318	FULL	Memory buffer
CRYPTO_MEM_BUFF199	0x4010831C	FULL	Memory buffer
CRYPTO_MEM_BUFF200	0x40108320	FULL	Memory buffer
CRYPTO_MEM_BUFF201	0x40108324	FULL	Memory buffer
CRYPTO_MEM_BUFF202	0x40108328	FULL	Memory buffer
CRYPTO_MEM_BUFF203	0x4010832C	FULL	Memory buffer
CRYPTO_MEM_BUFF204	0x40108330	FULL	Memory buffer
CRYPTO_MEM_BUFF205	0x40108334	FULL	Memory buffer
CRYPTO_MEM_BUFF206	0x40108338	FULL	Memory buffer
CRYPTO_MEM_BUFF207	0x4010833C	FULL	Memory buffer
CRYPTO_MEM_BUFF208	0x40108340	FULL	Memory buffer
CRYPTO_MEM_BUFF209	0x40108344	FULL	Memory buffer
CRYPTO_MEM_BUFF210	0x40108348	FULL	Memory buffer
CRYPTO_MEM_BUFF211	0x4010834C	FULL	Memory buffer
CRYPTO_MEM_BUFF212	0x40108350	FULL	Memory buffer
CRYPTO_MEM_BUFF213	0x40108354	FULL	Memory buffer
CRYPTO_MEM_BUFF214	0x40108358	FULL	Memory buffer
CRYPTO_MEM_BUFF215	0x4010835C	FULL	Memory buffer
CRYPTO_MEM_BUFF216	0x40108360	FULL	Memory buffer
CRYPTO_MEM_BUFF217	0x40108364	FULL	Memory buffer
CRYPTO_MEM_BUFF218	0x40108368	FULL	Memory buffer
CRYPTO_MEM_BUFF219	0x4010836C	FULL	Memory buffer
CRYPTO_MEM_BUFF220	0x40108370	FULL	Memory buffer
CRYPTO_MEM_BUFF221	0x40108374	FULL	Memory buffer
CRYPTO_MEM_BUFF222	0x40108378	FULL	Memory buffer
CRYPTO_MEM_BUFF223	0x4010837C	FULL	Memory buffer
CRYPTO_MEM_BUFF224	0x40108380	FULL	Memory buffer
CRYPTO_MEM_BUFF225	0x40108384	FULL	Memory buffer
CRYPTO_MEM_BUFF226	0x40108388	FULL	Memory buffer
CRYPTO_MEM_BUFF227	0x4010838C	FULL	Memory buffer
CRYPTO_MEM_BUFF228	0x40108390	FULL	Memory buffer
CRYPTO_MEM_BUFF229	0x40108394	FULL	Memory buffer
CRYPTO_MEM_BUFF230	0x40108398	FULL	Memory buffer
CRYPTO_MEM_BUFF231	0x4010839C	FULL	Memory buffer
CRYPTO_MEM_BUFF232	0x401083A0	FULL	Memory buffer
CRYPTO_MEM_BUFF233	0x401083A4	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF234	0x401083A8	FULL	Memory buffer
CRYPTO_MEM_BUFF235	0x401083AC	FULL	Memory buffer
CRYPTO_MEM_BUFF236	0x401083B0	FULL	Memory buffer
CRYPTO_MEM_BUFF237	0x401083B4	FULL	Memory buffer
CRYPTO_MEM_BUFF238	0x401083B8	FULL	Memory buffer
CRYPTO_MEM_BUFF239	0x401083BC	FULL	Memory buffer
CRYPTO_MEM_BUFF240	0x401083C0	FULL	Memory buffer
CRYPTO_MEM_BUFF241	0x401083C4	FULL	Memory buffer
CRYPTO_MEM_BUFF242	0x401083C8	FULL	Memory buffer
CRYPTO_MEM_BUFF243	0x401083CC	FULL	Memory buffer
CRYPTO_MEM_BUFF244	0x401083D0	FULL	Memory buffer
CRYPTO_MEM_BUFF245	0x401083D4	FULL	Memory buffer
CRYPTO_MEM_BUFF246	0x401083D8	FULL	Memory buffer
CRYPTO_MEM_BUFF247	0x401083DC	FULL	Memory buffer
CRYPTO_MEM_BUFF248	0x401083E0	FULL	Memory buffer
CRYPTO_MEM_BUFF249	0x401083E4	FULL	Memory buffer
CRYPTO_MEM_BUFF250	0x401083E8	FULL	Memory buffer
CRYPTO_MEM_BUFF251	0x401083EC	FULL	Memory buffer
CRYPTO_MEM_BUFF252	0x401083F0	FULL	Memory buffer
CRYPTO_MEM_BUFF253	0x401083F4	FULL	Memory buffer
CRYPTO_MEM_BUFF254	0x401083F8	FULL	Memory buffer
CRYPTO_MEM_BUFF255	0x401083FC	FULL	Memory buffer
CRYPTO_MEM_BUFF256	0x40108400	FULL	Memory buffer
CRYPTO_MEM_BUFF257	0x40108404	FULL	Memory buffer
CRYPTO_MEM_BUFF258	0x40108408	FULL	Memory buffer
CRYPTO_MEM_BUFF259	0x4010840C	FULL	Memory buffer
CRYPTO_MEM_BUFF260	0x40108410	FULL	Memory buffer
CRYPTO_MEM_BUFF261	0x40108414	FULL	Memory buffer
CRYPTO_MEM_BUFF262	0x40108418	FULL	Memory buffer
CRYPTO_MEM_BUFF263	0x4010841C	FULL	Memory buffer
CRYPTO_MEM_BUFF264	0x40108420	FULL	Memory buffer
CRYPTO_MEM_BUFF265	0x40108424	FULL	Memory buffer
CRYPTO_MEM_BUFF266	0x40108428	FULL	Memory buffer
CRYPTO_MEM_BUFF267	0x4010842C	FULL	Memory buffer
CRYPTO_MEM_BUFF268	0x40108430	FULL	Memory buffer
CRYPTO_MEM_BUFF269	0x40108434	FULL	Memory buffer
CRYPTO_MEM_BUFF270	0x40108438	FULL	Memory buffer
CRYPTO_MEM_BUFF271	0x4010843C	FULL	Memory buffer
CRYPTO_MEM_BUFF272	0x40108440	FULL	Memory buffer
CRYPTO_MEM_BUFF273	0x40108444	FULL	Memory buffer
CRYPTO_MEM_BUFF274	0x40108448	FULL	Memory buffer
CRYPTO_MEM_BUFF275	0x4010844C	FULL	Memory buffer
CRYPTO_MEM_BUFF276	0x40108450	FULL	Memory buffer
CRYPTO_MEM_BUFF277	0x40108454	FULL	Memory buffer
CRYPTO_MEM_BUFF278	0x40108458	FULL	Memory buffer
CRYPTO_MEM_BUFF279	0x4010845C	FULL	Memory buffer
CRYPTO_MEM_BUFF280	0x40108460	FULL	Memory buffer
CRYPTO_MEM_BUFF281	0x40108464	FULL	Memory buffer
CRYPTO_MEM_BUFF282	0x40108468	FULL	Memory buffer
CRYPTO_MEM_BUFF283	0x4010846C	FULL	Memory buffer
CRYPTO_MEM_BUFF284	0x40108470	FULL	Memory buffer
CRYPTO_MEM_BUFF285	0x40108474	FULL	Memory buffer
CRYPTO_MEM_BUFF286	0x40108478	FULL	Memory buffer
CRYPTO_MEM_BUFF287	0x4010847C	FULL	Memory buffer
CRYPTO_MEM_BUFF288	0x40108480	FULL	Memory buffer
CRYPTO_MEM_BUFF289	0x40108484	FULL	Memory buffer
CRYPTO_MEM_BUFF290	0x40108488	FULL	Memory buffer
CRYPTO_MEM_BUFF291	0x4010848C	FULL	Memory buffer
CRYPTO_MEM_BUFF292	0x40108490	FULL	Memory buffer
CRYPTO_MEM_BUFF293	0x40108494	FULL	Memory buffer
CRYPTO_MEM_BUFF294	0x40108498	FULL	Memory buffer
CRYPTO_MEM_BUFF295	0x4010849C	FULL	Memory buffer
CRYPTO_MEM_BUFF296	0x401084A0	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF297	0x401084A4	FULL	Memory buffer
CRYPTO_MEM_BUFF298	0x401084A8	FULL	Memory buffer
CRYPTO_MEM_BUFF299	0x401084AC	FULL	Memory buffer
CRYPTO_MEM_BUFF300	0x401084B0	FULL	Memory buffer
CRYPTO_MEM_BUFF301	0x401084B4	FULL	Memory buffer
CRYPTO_MEM_BUFF302	0x401084B8	FULL	Memory buffer
CRYPTO_MEM_BUFF303	0x401084BC	FULL	Memory buffer
CRYPTO_MEM_BUFF304	0x401084C0	FULL	Memory buffer
CRYPTO_MEM_BUFF305	0x401084C4	FULL	Memory buffer
CRYPTO_MEM_BUFF306	0x401084C8	FULL	Memory buffer
CRYPTO_MEM_BUFF307	0x401084CC	FULL	Memory buffer
CRYPTO_MEM_BUFF308	0x401084D0	FULL	Memory buffer
CRYPTO_MEM_BUFF309	0x401084D4	FULL	Memory buffer
CRYPTO_MEM_BUFF310	0x401084D8	FULL	Memory buffer
CRYPTO_MEM_BUFF311	0x401084DC	FULL	Memory buffer
CRYPTO_MEM_BUFF312	0x401084E0	FULL	Memory buffer
CRYPTO_MEM_BUFF313	0x401084E4	FULL	Memory buffer
CRYPTO_MEM_BUFF314	0x401084E8	FULL	Memory buffer
CRYPTO_MEM_BUFF315	0x401084EC	FULL	Memory buffer
CRYPTO_MEM_BUFF316	0x401084F0	FULL	Memory buffer
CRYPTO_MEM_BUFF317	0x401084F4	FULL	Memory buffer
CRYPTO_MEM_BUFF318	0x401084F8	FULL	Memory buffer
CRYPTO_MEM_BUFF319	0x401084FC	FULL	Memory buffer
CRYPTO_MEM_BUFF320	0x40108500	FULL	Memory buffer
CRYPTO_MEM_BUFF321	0x40108504	FULL	Memory buffer
CRYPTO_MEM_BUFF322	0x40108508	FULL	Memory buffer
CRYPTO_MEM_BUFF323	0x4010850C	FULL	Memory buffer
CRYPTO_MEM_BUFF324	0x40108510	FULL	Memory buffer
CRYPTO_MEM_BUFF325	0x40108514	FULL	Memory buffer
CRYPTO_MEM_BUFF326	0x40108518	FULL	Memory buffer
CRYPTO_MEM_BUFF327	0x4010851C	FULL	Memory buffer
CRYPTO_MEM_BUFF328	0x40108520	FULL	Memory buffer
CRYPTO_MEM_BUFF329	0x40108524	FULL	Memory buffer
CRYPTO_MEM_BUFF330	0x40108528	FULL	Memory buffer
CRYPTO_MEM_BUFF331	0x4010852C	FULL	Memory buffer
CRYPTO_MEM_BUFF332	0x40108530	FULL	Memory buffer
CRYPTO_MEM_BUFF333	0x40108534	FULL	Memory buffer
CRYPTO_MEM_BUFF334	0x40108538	FULL	Memory buffer
CRYPTO_MEM_BUFF335	0x4010853C	FULL	Memory buffer
CRYPTO_MEM_BUFF336	0x40108540	FULL	Memory buffer
CRYPTO_MEM_BUFF337	0x40108544	FULL	Memory buffer
CRYPTO_MEM_BUFF338	0x40108548	FULL	Memory buffer
CRYPTO_MEM_BUFF339	0x4010854C	FULL	Memory buffer
CRYPTO_MEM_BUFF340	0x40108550	FULL	Memory buffer
CRYPTO_MEM_BUFF341	0x40108554	FULL	Memory buffer
CRYPTO_MEM_BUFF342	0x40108558	FULL	Memory buffer
CRYPTO_MEM_BUFF343	0x4010855C	FULL	Memory buffer
CRYPTO_MEM_BUFF344	0x40108560	FULL	Memory buffer
CRYPTO_MEM_BUFF345	0x40108564	FULL	Memory buffer
CRYPTO_MEM_BUFF346	0x40108568	FULL	Memory buffer
CRYPTO_MEM_BUFF347	0x4010856C	FULL	Memory buffer
CRYPTO_MEM_BUFF348	0x40108570	FULL	Memory buffer
CRYPTO_MEM_BUFF349	0x40108574	FULL	Memory buffer
CRYPTO_MEM_BUFF350	0x40108578	FULL	Memory buffer
CRYPTO_MEM_BUFF351	0x4010857C	FULL	Memory buffer
CRYPTO_MEM_BUFF352	0x40108580	FULL	Memory buffer
CRYPTO_MEM_BUFF353	0x40108584	FULL	Memory buffer
CRYPTO_MEM_BUFF354	0x40108588	FULL	Memory buffer
CRYPTO_MEM_BUFF355	0x4010858C	FULL	Memory buffer
CRYPTO_MEM_BUFF356	0x40108590	FULL	Memory buffer
CRYPTO_MEM_BUFF357	0x40108594	FULL	Memory buffer
CRYPTO_MEM_BUFF358	0x40108598	FULL	Memory buffer
CRYPTO_MEM_BUFF359	0x4010859C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF360	0x401085A0	FULL	Memory buffer
CRYPTO_MEM_BUFF361	0x401085A4	FULL	Memory buffer
CRYPTO_MEM_BUFF362	0x401085A8	FULL	Memory buffer
CRYPTO_MEM_BUFF363	0x401085AC	FULL	Memory buffer
CRYPTO_MEM_BUFF364	0x401085B0	FULL	Memory buffer
CRYPTO_MEM_BUFF365	0x401085B4	FULL	Memory buffer
CRYPTO_MEM_BUFF366	0x401085B8	FULL	Memory buffer
CRYPTO_MEM_BUFF367	0x401085BC	FULL	Memory buffer
CRYPTO_MEM_BUFF368	0x401085C0	FULL	Memory buffer
CRYPTO_MEM_BUFF369	0x401085C4	FULL	Memory buffer
CRYPTO_MEM_BUFF370	0x401085C8	FULL	Memory buffer
CRYPTO_MEM_BUFF371	0x401085CC	FULL	Memory buffer
CRYPTO_MEM_BUFF372	0x401085D0	FULL	Memory buffer
CRYPTO_MEM_BUFF373	0x401085D4	FULL	Memory buffer
CRYPTO_MEM_BUFF374	0x401085D8	FULL	Memory buffer
CRYPTO_MEM_BUFF375	0x401085DC	FULL	Memory buffer
CRYPTO_MEM_BUFF376	0x401085E0	FULL	Memory buffer
CRYPTO_MEM_BUFF377	0x401085E4	FULL	Memory buffer
CRYPTO_MEM_BUFF378	0x401085E8	FULL	Memory buffer
CRYPTO_MEM_BUFF379	0x401085EC	FULL	Memory buffer
CRYPTO_MEM_BUFF380	0x401085F0	FULL	Memory buffer
CRYPTO_MEM_BUFF381	0x401085F4	FULL	Memory buffer
CRYPTO_MEM_BUFF382	0x401085F8	FULL	Memory buffer
CRYPTO_MEM_BUFF383	0x401085FC	FULL	Memory buffer
CRYPTO_MEM_BUFF384	0x40108600	FULL	Memory buffer
CRYPTO_MEM_BUFF385	0x40108604	FULL	Memory buffer
CRYPTO_MEM_BUFF386	0x40108608	FULL	Memory buffer
CRYPTO_MEM_BUFF387	0x4010860C	FULL	Memory buffer
CRYPTO_MEM_BUFF388	0x40108610	FULL	Memory buffer
CRYPTO_MEM_BUFF389	0x40108614	FULL	Memory buffer
CRYPTO_MEM_BUFF390	0x40108618	FULL	Memory buffer
CRYPTO_MEM_BUFF391	0x4010861C	FULL	Memory buffer
CRYPTO_MEM_BUFF392	0x40108620	FULL	Memory buffer
CRYPTO_MEM_BUFF393	0x40108624	FULL	Memory buffer
CRYPTO_MEM_BUFF394	0x40108628	FULL	Memory buffer
CRYPTO_MEM_BUFF395	0x4010862C	FULL	Memory buffer
CRYPTO_MEM_BUFF396	0x40108630	FULL	Memory buffer
CRYPTO_MEM_BUFF397	0x40108634	FULL	Memory buffer
CRYPTO_MEM_BUFF398	0x40108638	FULL	Memory buffer
CRYPTO_MEM_BUFF399	0x4010863C	FULL	Memory buffer
CRYPTO_MEM_BUFF400	0x40108640	FULL	Memory buffer
CRYPTO_MEM_BUFF401	0x40108644	FULL	Memory buffer
CRYPTO_MEM_BUFF402	0x40108648	FULL	Memory buffer
CRYPTO_MEM_BUFF403	0x4010864C	FULL	Memory buffer
CRYPTO_MEM_BUFF404	0x40108650	FULL	Memory buffer
CRYPTO_MEM_BUFF405	0x40108654	FULL	Memory buffer
CRYPTO_MEM_BUFF406	0x40108658	FULL	Memory buffer
CRYPTO_MEM_BUFF407	0x4010865C	FULL	Memory buffer
CRYPTO_MEM_BUFF408	0x40108660	FULL	Memory buffer
CRYPTO_MEM_BUFF409	0x40108664	FULL	Memory buffer
CRYPTO_MEM_BUFF410	0x40108668	FULL	Memory buffer
CRYPTO_MEM_BUFF411	0x4010866C	FULL	Memory buffer
CRYPTO_MEM_BUFF412	0x40108670	FULL	Memory buffer
CRYPTO_MEM_BUFF413	0x40108674	FULL	Memory buffer
CRYPTO_MEM_BUFF414	0x40108678	FULL	Memory buffer
CRYPTO_MEM_BUFF415	0x4010867C	FULL	Memory buffer
CRYPTO_MEM_BUFF416	0x40108680	FULL	Memory buffer
CRYPTO_MEM_BUFF417	0x40108684	FULL	Memory buffer
CRYPTO_MEM_BUFF418	0x40108688	FULL	Memory buffer
CRYPTO_MEM_BUFF419	0x4010868C	FULL	Memory buffer
CRYPTO_MEM_BUFF420	0x40108690	FULL	Memory buffer
CRYPTO_MEM_BUFF421	0x40108694	FULL	Memory buffer
CRYPTO_MEM_BUFF422	0x40108698	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF423	0x4010869C	FULL	Memory buffer
CRYPTO_MEM_BUFF424	0x401086A0	FULL	Memory buffer
CRYPTO_MEM_BUFF425	0x401086A4	FULL	Memory buffer
CRYPTO_MEM_BUFF426	0x401086A8	FULL	Memory buffer
CRYPTO_MEM_BUFF427	0x401086AC	FULL	Memory buffer
CRYPTO_MEM_BUFF428	0x401086B0	FULL	Memory buffer
CRYPTO_MEM_BUFF429	0x401086B4	FULL	Memory buffer
CRYPTO_MEM_BUFF430	0x401086B8	FULL	Memory buffer
CRYPTO_MEM_BUFF431	0x401086BC	FULL	Memory buffer
CRYPTO_MEM_BUFF432	0x401086C0	FULL	Memory buffer
CRYPTO_MEM_BUFF433	0x401086C4	FULL	Memory buffer
CRYPTO_MEM_BUFF434	0x401086C8	FULL	Memory buffer
CRYPTO_MEM_BUFF435	0x401086CC	FULL	Memory buffer
CRYPTO_MEM_BUFF436	0x401086D0	FULL	Memory buffer
CRYPTO_MEM_BUFF437	0x401086D4	FULL	Memory buffer
CRYPTO_MEM_BUFF438	0x401086D8	FULL	Memory buffer
CRYPTO_MEM_BUFF439	0x401086DC	FULL	Memory buffer
CRYPTO_MEM_BUFF440	0x401086E0	FULL	Memory buffer
CRYPTO_MEM_BUFF441	0x401086E4	FULL	Memory buffer
CRYPTO_MEM_BUFF442	0x401086E8	FULL	Memory buffer
CRYPTO_MEM_BUFF443	0x401086EC	FULL	Memory buffer
CRYPTO_MEM_BUFF444	0x401086F0	FULL	Memory buffer
CRYPTO_MEM_BUFF445	0x401086F4	FULL	Memory buffer
CRYPTO_MEM_BUFF446	0x401086F8	FULL	Memory buffer
CRYPTO_MEM_BUFF447	0x401086FC	FULL	Memory buffer
CRYPTO_MEM_BUFF448	0x40108700	FULL	Memory buffer
CRYPTO_MEM_BUFF449	0x40108704	FULL	Memory buffer
CRYPTO_MEM_BUFF450	0x40108708	FULL	Memory buffer
CRYPTO_MEM_BUFF451	0x4010870C	FULL	Memory buffer
CRYPTO_MEM_BUFF452	0x40108710	FULL	Memory buffer
CRYPTO_MEM_BUFF453	0x40108714	FULL	Memory buffer
CRYPTO_MEM_BUFF454	0x40108718	FULL	Memory buffer
CRYPTO_MEM_BUFF455	0x4010871C	FULL	Memory buffer
CRYPTO_MEM_BUFF456	0x40108720	FULL	Memory buffer
CRYPTO_MEM_BUFF457	0x40108724	FULL	Memory buffer
CRYPTO_MEM_BUFF458	0x40108728	FULL	Memory buffer
CRYPTO_MEM_BUFF459	0x4010872C	FULL	Memory buffer
CRYPTO_MEM_BUFF460	0x40108730	FULL	Memory buffer
CRYPTO_MEM_BUFF461	0x40108734	FULL	Memory buffer
CRYPTO_MEM_BUFF462	0x40108738	FULL	Memory buffer
CRYPTO_MEM_BUFF463	0x4010873C	FULL	Memory buffer
CRYPTO_MEM_BUFF464	0x40108740	FULL	Memory buffer
CRYPTO_MEM_BUFF465	0x40108744	FULL	Memory buffer
CRYPTO_MEM_BUFF466	0x40108748	FULL	Memory buffer
CRYPTO_MEM_BUFF467	0x4010874C	FULL	Memory buffer
CRYPTO_MEM_BUFF468	0x40108750	FULL	Memory buffer
CRYPTO_MEM_BUFF469	0x40108754	FULL	Memory buffer
CRYPTO_MEM_BUFF470	0x40108758	FULL	Memory buffer
CRYPTO_MEM_BUFF471	0x4010875C	FULL	Memory buffer
CRYPTO_MEM_BUFF472	0x40108760	FULL	Memory buffer
CRYPTO_MEM_BUFF473	0x40108764	FULL	Memory buffer
CRYPTO_MEM_BUFF474	0x40108768	FULL	Memory buffer
CRYPTO_MEM_BUFF475	0x4010876C	FULL	Memory buffer
CRYPTO_MEM_BUFF476	0x40108770	FULL	Memory buffer
CRYPTO_MEM_BUFF477	0x40108774	FULL	Memory buffer
CRYPTO_MEM_BUFF478	0x40108778	FULL	Memory buffer
CRYPTO_MEM_BUFF479	0x4010877C	FULL	Memory buffer
CRYPTO_MEM_BUFF480	0x40108780	FULL	Memory buffer
CRYPTO_MEM_BUFF481	0x40108784	FULL	Memory buffer
CRYPTO_MEM_BUFF482	0x40108788	FULL	Memory buffer
CRYPTO_MEM_BUFF483	0x4010878C	FULL	Memory buffer
CRYPTO_MEM_BUFF484	0x40108790	FULL	Memory buffer
CRYPTO_MEM_BUFF485	0x40108794	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF486	0x40108798	FULL	Memory buffer
CRYPTO_MEM_BUFF487	0x4010879C	FULL	Memory buffer
CRYPTO_MEM_BUFF488	0x401087A0	FULL	Memory buffer
CRYPTO_MEM_BUFF489	0x401087A4	FULL	Memory buffer
CRYPTO_MEM_BUFF490	0x401087A8	FULL	Memory buffer
CRYPTO_MEM_BUFF491	0x401087AC	FULL	Memory buffer
CRYPTO_MEM_BUFF492	0x401087B0	FULL	Memory buffer
CRYPTO_MEM_BUFF493	0x401087B4	FULL	Memory buffer
CRYPTO_MEM_BUFF494	0x401087B8	FULL	Memory buffer
CRYPTO_MEM_BUFF495	0x401087BC	FULL	Memory buffer
CRYPTO_MEM_BUFF496	0x401087C0	FULL	Memory buffer
CRYPTO_MEM_BUFF497	0x401087C4	FULL	Memory buffer
CRYPTO_MEM_BUFF498	0x401087C8	FULL	Memory buffer
CRYPTO_MEM_BUFF499	0x401087CC	FULL	Memory buffer
CRYPTO_MEM_BUFF500	0x401087D0	FULL	Memory buffer
CRYPTO_MEM_BUFF501	0x401087D4	FULL	Memory buffer
CRYPTO_MEM_BUFF502	0x401087D8	FULL	Memory buffer
CRYPTO_MEM_BUFF503	0x401087DC	FULL	Memory buffer
CRYPTO_MEM_BUFF504	0x401087E0	FULL	Memory buffer
CRYPTO_MEM_BUFF505	0x401087E4	FULL	Memory buffer
CRYPTO_MEM_BUFF506	0x401087E8	FULL	Memory buffer
CRYPTO_MEM_BUFF507	0x401087EC	FULL	Memory buffer
CRYPTO_MEM_BUFF508	0x401087F0	FULL	Memory buffer
CRYPTO_MEM_BUFF509	0x401087F4	FULL	Memory buffer
CRYPTO_MEM_BUFF510	0x401087F8	FULL	Memory buffer
CRYPTO_MEM_BUFF511	0x401087FC	FULL	Memory buffer
CRYPTO_MEM_BUFF512	0x40108800	FULL	Memory buffer
CRYPTO_MEM_BUFF513	0x40108804	FULL	Memory buffer
CRYPTO_MEM_BUFF514	0x40108808	FULL	Memory buffer
CRYPTO_MEM_BUFF515	0x4010880C	FULL	Memory buffer
CRYPTO_MEM_BUFF516	0x40108810	FULL	Memory buffer
CRYPTO_MEM_BUFF517	0x40108814	FULL	Memory buffer
CRYPTO_MEM_BUFF518	0x40108818	FULL	Memory buffer
CRYPTO_MEM_BUFF519	0x4010881C	FULL	Memory buffer
CRYPTO_MEM_BUFF520	0x40108820	FULL	Memory buffer
CRYPTO_MEM_BUFF521	0x40108824	FULL	Memory buffer
CRYPTO_MEM_BUFF522	0x40108828	FULL	Memory buffer
CRYPTO_MEM_BUFF523	0x4010882C	FULL	Memory buffer
CRYPTO_MEM_BUFF524	0x40108830	FULL	Memory buffer
CRYPTO_MEM_BUFF525	0x40108834	FULL	Memory buffer
CRYPTO_MEM_BUFF526	0x40108838	FULL	Memory buffer
CRYPTO_MEM_BUFF527	0x4010883C	FULL	Memory buffer
CRYPTO_MEM_BUFF528	0x40108840	FULL	Memory buffer
CRYPTO_MEM_BUFF529	0x40108844	FULL	Memory buffer
CRYPTO_MEM_BUFF530	0x40108848	FULL	Memory buffer
CRYPTO_MEM_BUFF531	0x4010884C	FULL	Memory buffer
CRYPTO_MEM_BUFF532	0x40108850	FULL	Memory buffer
CRYPTO_MEM_BUFF533	0x40108854	FULL	Memory buffer
CRYPTO_MEM_BUFF534	0x40108858	FULL	Memory buffer
CRYPTO_MEM_BUFF535	0x4010885C	FULL	Memory buffer
CRYPTO_MEM_BUFF536	0x40108860	FULL	Memory buffer
CRYPTO_MEM_BUFF537	0x40108864	FULL	Memory buffer
CRYPTO_MEM_BUFF538	0x40108868	FULL	Memory buffer
CRYPTO_MEM_BUFF539	0x4010886C	FULL	Memory buffer
CRYPTO_MEM_BUFF540	0x40108870	FULL	Memory buffer
CRYPTO_MEM_BUFF541	0x40108874	FULL	Memory buffer
CRYPTO_MEM_BUFF542	0x40108878	FULL	Memory buffer
CRYPTO_MEM_BUFF543	0x4010887C	FULL	Memory buffer
CRYPTO_MEM_BUFF544	0x40108880	FULL	Memory buffer
CRYPTO_MEM_BUFF545	0x40108884	FULL	Memory buffer
CRYPTO_MEM_BUFF546	0x40108888	FULL	Memory buffer
CRYPTO_MEM_BUFF547	0x4010888C	FULL	Memory buffer
CRYPTO_MEM_BUFF548	0x40108890	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF549	0x40108894	FULL	Memory buffer
CRYPTO_MEM_BUFF550	0x40108898	FULL	Memory buffer
CRYPTO_MEM_BUFF551	0x4010889C	FULL	Memory buffer
CRYPTO_MEM_BUFF552	0x401088A0	FULL	Memory buffer
CRYPTO_MEM_BUFF553	0x401088A4	FULL	Memory buffer
CRYPTO_MEM_BUFF554	0x401088A8	FULL	Memory buffer
CRYPTO_MEM_BUFF555	0x401088AC	FULL	Memory buffer
CRYPTO_MEM_BUFF556	0x401088B0	FULL	Memory buffer
CRYPTO_MEM_BUFF557	0x401088B4	FULL	Memory buffer
CRYPTO_MEM_BUFF558	0x401088B8	FULL	Memory buffer
CRYPTO_MEM_BUFF559	0x401088BC	FULL	Memory buffer
CRYPTO_MEM_BUFF560	0x401088C0	FULL	Memory buffer
CRYPTO_MEM_BUFF561	0x401088C4	FULL	Memory buffer
CRYPTO_MEM_BUFF562	0x401088C8	FULL	Memory buffer
CRYPTO_MEM_BUFF563	0x401088CC	FULL	Memory buffer
CRYPTO_MEM_BUFF564	0x401088D0	FULL	Memory buffer
CRYPTO_MEM_BUFF565	0x401088D4	FULL	Memory buffer
CRYPTO_MEM_BUFF566	0x401088D8	FULL	Memory buffer
CRYPTO_MEM_BUFF567	0x401088DC	FULL	Memory buffer
CRYPTO_MEM_BUFF568	0x401088E0	FULL	Memory buffer
CRYPTO_MEM_BUFF569	0x401088E4	FULL	Memory buffer
CRYPTO_MEM_BUFF570	0x401088E8	FULL	Memory buffer
CRYPTO_MEM_BUFF571	0x401088EC	FULL	Memory buffer
CRYPTO_MEM_BUFF572	0x401088F0	FULL	Memory buffer
CRYPTO_MEM_BUFF573	0x401088F4	FULL	Memory buffer
CRYPTO_MEM_BUFF574	0x401088F8	FULL	Memory buffer
CRYPTO_MEM_BUFF575	0x401088FC	FULL	Memory buffer
CRYPTO_MEM_BUFF576	0x40108900	FULL	Memory buffer
CRYPTO_MEM_BUFF577	0x40108904	FULL	Memory buffer
CRYPTO_MEM_BUFF578	0x40108908	FULL	Memory buffer
CRYPTO_MEM_BUFF579	0x4010890C	FULL	Memory buffer
CRYPTO_MEM_BUFF580	0x40108910	FULL	Memory buffer
CRYPTO_MEM_BUFF581	0x40108914	FULL	Memory buffer
CRYPTO_MEM_BUFF582	0x40108918	FULL	Memory buffer
CRYPTO_MEM_BUFF583	0x4010891C	FULL	Memory buffer
CRYPTO_MEM_BUFF584	0x40108920	FULL	Memory buffer
CRYPTO_MEM_BUFF585	0x40108924	FULL	Memory buffer
CRYPTO_MEM_BUFF586	0x40108928	FULL	Memory buffer
CRYPTO_MEM_BUFF587	0x4010892C	FULL	Memory buffer
CRYPTO_MEM_BUFF588	0x40108930	FULL	Memory buffer
CRYPTO_MEM_BUFF589	0x40108934	FULL	Memory buffer
CRYPTO_MEM_BUFF590	0x40108938	FULL	Memory buffer
CRYPTO_MEM_BUFF591	0x4010893C	FULL	Memory buffer
CRYPTO_MEM_BUFF592	0x40108940	FULL	Memory buffer
CRYPTO_MEM_BUFF593	0x40108944	FULL	Memory buffer
CRYPTO_MEM_BUFF594	0x40108948	FULL	Memory buffer
CRYPTO_MEM_BUFF595	0x4010894C	FULL	Memory buffer
CRYPTO_MEM_BUFF596	0x40108950	FULL	Memory buffer
CRYPTO_MEM_BUFF597	0x40108954	FULL	Memory buffer
CRYPTO_MEM_BUFF598	0x40108958	FULL	Memory buffer
CRYPTO_MEM_BUFF599	0x4010895C	FULL	Memory buffer
CRYPTO_MEM_BUFF600	0x40108960	FULL	Memory buffer
CRYPTO_MEM_BUFF601	0x40108964	FULL	Memory buffer
CRYPTO_MEM_BUFF602	0x40108968	FULL	Memory buffer
CRYPTO_MEM_BUFF603	0x4010896C	FULL	Memory buffer
CRYPTO_MEM_BUFF604	0x40108970	FULL	Memory buffer
CRYPTO_MEM_BUFF605	0x40108974	FULL	Memory buffer
CRYPTO_MEM_BUFF606	0x40108978	FULL	Memory buffer
CRYPTO_MEM_BUFF607	0x4010897C	FULL	Memory buffer
CRYPTO_MEM_BUFF608	0x40108980	FULL	Memory buffer
CRYPTO_MEM_BUFF609	0x40108984	FULL	Memory buffer
CRYPTO_MEM_BUFF610	0x40108988	FULL	Memory buffer
CRYPTO_MEM_BUFF611	0x4010898C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF612	0x40108990	FULL	Memory buffer
CRYPTO_MEM_BUFF613	0x40108994	FULL	Memory buffer
CRYPTO_MEM_BUFF614	0x40108998	FULL	Memory buffer
CRYPTO_MEM_BUFF615	0x4010899C	FULL	Memory buffer
CRYPTO_MEM_BUFF616	0x401089A0	FULL	Memory buffer
CRYPTO_MEM_BUFF617	0x401089A4	FULL	Memory buffer
CRYPTO_MEM_BUFF618	0x401089A8	FULL	Memory buffer
CRYPTO_MEM_BUFF619	0x401089AC	FULL	Memory buffer
CRYPTO_MEM_BUFF620	0x401089B0	FULL	Memory buffer
CRYPTO_MEM_BUFF621	0x401089B4	FULL	Memory buffer
CRYPTO_MEM_BUFF622	0x401089B8	FULL	Memory buffer
CRYPTO_MEM_BUFF623	0x401089BC	FULL	Memory buffer
CRYPTO_MEM_BUFF624	0x401089C0	FULL	Memory buffer
CRYPTO_MEM_BUFF625	0x401089C4	FULL	Memory buffer
CRYPTO_MEM_BUFF626	0x401089C8	FULL	Memory buffer
CRYPTO_MEM_BUFF627	0x401089CC	FULL	Memory buffer
CRYPTO_MEM_BUFF628	0x401089D0	FULL	Memory buffer
CRYPTO_MEM_BUFF629	0x401089D4	FULL	Memory buffer
CRYPTO_MEM_BUFF630	0x401089D8	FULL	Memory buffer
CRYPTO_MEM_BUFF631	0x401089DC	FULL	Memory buffer
CRYPTO_MEM_BUFF632	0x401089E0	FULL	Memory buffer
CRYPTO_MEM_BUFF633	0x401089E4	FULL	Memory buffer
CRYPTO_MEM_BUFF634	0x401089E8	FULL	Memory buffer
CRYPTO_MEM_BUFF635	0x401089EC	FULL	Memory buffer
CRYPTO_MEM_BUFF636	0x401089F0	FULL	Memory buffer
CRYPTO_MEM_BUFF637	0x401089F4	FULL	Memory buffer
CRYPTO_MEM_BUFF638	0x401089F8	FULL	Memory buffer
CRYPTO_MEM_BUFF639	0x401089FC	FULL	Memory buffer
CRYPTO_MEM_BUFF640	0x40108A00	FULL	Memory buffer
CRYPTO_MEM_BUFF641	0x40108A04	FULL	Memory buffer
CRYPTO_MEM_BUFF642	0x40108A08	FULL	Memory buffer
CRYPTO_MEM_BUFF643	0x40108A0C	FULL	Memory buffer
CRYPTO_MEM_BUFF644	0x40108A10	FULL	Memory buffer
CRYPTO_MEM_BUFF645	0x40108A14	FULL	Memory buffer
CRYPTO_MEM_BUFF646	0x40108A18	FULL	Memory buffer
CRYPTO_MEM_BUFF647	0x40108A1C	FULL	Memory buffer
CRYPTO_MEM_BUFF648	0x40108A20	FULL	Memory buffer
CRYPTO_MEM_BUFF649	0x40108A24	FULL	Memory buffer
CRYPTO_MEM_BUFF650	0x40108A28	FULL	Memory buffer
CRYPTO_MEM_BUFF651	0x40108A2C	FULL	Memory buffer
CRYPTO_MEM_BUFF652	0x40108A30	FULL	Memory buffer
CRYPTO_MEM_BUFF653	0x40108A34	FULL	Memory buffer
CRYPTO_MEM_BUFF654	0x40108A38	FULL	Memory buffer
CRYPTO_MEM_BUFF655	0x40108A3C	FULL	Memory buffer
CRYPTO_MEM_BUFF656	0x40108A40	FULL	Memory buffer
CRYPTO_MEM_BUFF657	0x40108A44	FULL	Memory buffer
CRYPTO_MEM_BUFF658	0x40108A48	FULL	Memory buffer
CRYPTO_MEM_BUFF659	0x40108A4C	FULL	Memory buffer
CRYPTO_MEM_BUFF660	0x40108A50	FULL	Memory buffer
CRYPTO_MEM_BUFF661	0x40108A54	FULL	Memory buffer
CRYPTO_MEM_BUFF662	0x40108A58	FULL	Memory buffer
CRYPTO_MEM_BUFF663	0x40108A5C	FULL	Memory buffer
CRYPTO_MEM_BUFF664	0x40108A60	FULL	Memory buffer
CRYPTO_MEM_BUFF665	0x40108A64	FULL	Memory buffer
CRYPTO_MEM_BUFF666	0x40108A68	FULL	Memory buffer
CRYPTO_MEM_BUFF667	0x40108A6C	FULL	Memory buffer
CRYPTO_MEM_BUFF668	0x40108A70	FULL	Memory buffer
CRYPTO_MEM_BUFF669	0x40108A74	FULL	Memory buffer
CRYPTO_MEM_BUFF670	0x40108A78	FULL	Memory buffer
CRYPTO_MEM_BUFF671	0x40108A7C	FULL	Memory buffer
CRYPTO_MEM_BUFF672	0x40108A80	FULL	Memory buffer
CRYPTO_MEM_BUFF673	0x40108A84	FULL	Memory buffer
CRYPTO_MEM_BUFF674	0x40108A88	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF675	0x40108A8C	FULL	Memory buffer
CRYPTO_MEM_BUFF676	0x40108A90	FULL	Memory buffer
CRYPTO_MEM_BUFF677	0x40108A94	FULL	Memory buffer
CRYPTO_MEM_BUFF678	0x40108A98	FULL	Memory buffer
CRYPTO_MEM_BUFF679	0x40108A9C	FULL	Memory buffer
CRYPTO_MEM_BUFF680	0x40108AA0	FULL	Memory buffer
CRYPTO_MEM_BUFF681	0x40108AA4	FULL	Memory buffer
CRYPTO_MEM_BUFF682	0x40108AA8	FULL	Memory buffer
CRYPTO_MEM_BUFF683	0x40108AAC	FULL	Memory buffer
CRYPTO_MEM_BUFF684	0x40108AB0	FULL	Memory buffer
CRYPTO_MEM_BUFF685	0x40108AB4	FULL	Memory buffer
CRYPTO_MEM_BUFF686	0x40108AB8	FULL	Memory buffer
CRYPTO_MEM_BUFF687	0x40108ABC	FULL	Memory buffer
CRYPTO_MEM_BUFF688	0x40108AC0	FULL	Memory buffer
CRYPTO_MEM_BUFF689	0x40108AC4	FULL	Memory buffer
CRYPTO_MEM_BUFF690	0x40108AC8	FULL	Memory buffer
CRYPTO_MEM_BUFF691	0x40108ACC	FULL	Memory buffer
CRYPTO_MEM_BUFF692	0x40108AD0	FULL	Memory buffer
CRYPTO_MEM_BUFF693	0x40108AD4	FULL	Memory buffer
CRYPTO_MEM_BUFF694	0x40108AD8	FULL	Memory buffer
CRYPTO_MEM_BUFF695	0x40108ADC	FULL	Memory buffer
CRYPTO_MEM_BUFF696	0x40108AE0	FULL	Memory buffer
CRYPTO_MEM_BUFF697	0x40108AE4	FULL	Memory buffer
CRYPTO_MEM_BUFF698	0x40108AE8	FULL	Memory buffer
CRYPTO_MEM_BUFF699	0x40108AEC	FULL	Memory buffer
CRYPTO_MEM_BUFF700	0x40108AF0	FULL	Memory buffer
CRYPTO_MEM_BUFF701	0x40108AF4	FULL	Memory buffer
CRYPTO_MEM_BUFF702	0x40108AF8	FULL	Memory buffer
CRYPTO_MEM_BUFF703	0x40108AFC	FULL	Memory buffer
CRYPTO_MEM_BUFF704	0x40108B00	FULL	Memory buffer
CRYPTO_MEM_BUFF705	0x40108B04	FULL	Memory buffer
CRYPTO_MEM_BUFF706	0x40108B08	FULL	Memory buffer
CRYPTO_MEM_BUFF707	0x40108B0C	FULL	Memory buffer
CRYPTO_MEM_BUFF708	0x40108B10	FULL	Memory buffer
CRYPTO_MEM_BUFF709	0x40108B14	FULL	Memory buffer
CRYPTO_MEM_BUFF710	0x40108B18	FULL	Memory buffer
CRYPTO_MEM_BUFF711	0x40108B1C	FULL	Memory buffer
CRYPTO_MEM_BUFF712	0x40108B20	FULL	Memory buffer
CRYPTO_MEM_BUFF713	0x40108B24	FULL	Memory buffer
CRYPTO_MEM_BUFF714	0x40108B28	FULL	Memory buffer
CRYPTO_MEM_BUFF715	0x40108B2C	FULL	Memory buffer
CRYPTO_MEM_BUFF716	0x40108B30	FULL	Memory buffer
CRYPTO_MEM_BUFF717	0x40108B34	FULL	Memory buffer
CRYPTO_MEM_BUFF718	0x40108B38	FULL	Memory buffer
CRYPTO_MEM_BUFF719	0x40108B3C	FULL	Memory buffer
CRYPTO_MEM_BUFF720	0x40108B40	FULL	Memory buffer
CRYPTO_MEM_BUFF721	0x40108B44	FULL	Memory buffer
CRYPTO_MEM_BUFF722	0x40108B48	FULL	Memory buffer
CRYPTO_MEM_BUFF723	0x40108B4C	FULL	Memory buffer
CRYPTO_MEM_BUFF724	0x40108B50	FULL	Memory buffer
CRYPTO_MEM_BUFF725	0x40108B54	FULL	Memory buffer
CRYPTO_MEM_BUFF726	0x40108B58	FULL	Memory buffer
CRYPTO_MEM_BUFF727	0x40108B5C	FULL	Memory buffer
CRYPTO_MEM_BUFF728	0x40108B60	FULL	Memory buffer
CRYPTO_MEM_BUFF729	0x40108B64	FULL	Memory buffer
CRYPTO_MEM_BUFF730	0x40108B68	FULL	Memory buffer
CRYPTO_MEM_BUFF731	0x40108B6C	FULL	Memory buffer
CRYPTO_MEM_BUFF732	0x40108B70	FULL	Memory buffer
CRYPTO_MEM_BUFF733	0x40108B74	FULL	Memory buffer
CRYPTO_MEM_BUFF734	0x40108B78	FULL	Memory buffer
CRYPTO_MEM_BUFF735	0x40108B7C	FULL	Memory buffer
CRYPTO_MEM_BUFF736	0x40108B80	FULL	Memory buffer
CRYPTO_MEM_BUFF737	0x40108B84	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF738	0x40108B88	FULL	Memory buffer
CRYPTO_MEM_BUFF739	0x40108B8C	FULL	Memory buffer
CRYPTO_MEM_BUFF740	0x40108B90	FULL	Memory buffer
CRYPTO_MEM_BUFF741	0x40108B94	FULL	Memory buffer
CRYPTO_MEM_BUFF742	0x40108B98	FULL	Memory buffer
CRYPTO_MEM_BUFF743	0x40108B9C	FULL	Memory buffer
CRYPTO_MEM_BUFF744	0x40108BA0	FULL	Memory buffer
CRYPTO_MEM_BUFF745	0x40108BA4	FULL	Memory buffer
CRYPTO_MEM_BUFF746	0x40108BA8	FULL	Memory buffer
CRYPTO_MEM_BUFF747	0x40108BAC	FULL	Memory buffer
CRYPTO_MEM_BUFF748	0x40108BB0	FULL	Memory buffer
CRYPTO_MEM_BUFF749	0x40108BB4	FULL	Memory buffer
CRYPTO_MEM_BUFF750	0x40108BB8	FULL	Memory buffer
CRYPTO_MEM_BUFF751	0x40108BBC	FULL	Memory buffer
CRYPTO_MEM_BUFF752	0x40108BC0	FULL	Memory buffer
CRYPTO_MEM_BUFF753	0x40108BC4	FULL	Memory buffer
CRYPTO_MEM_BUFF754	0x40108BC8	FULL	Memory buffer
CRYPTO_MEM_BUFF755	0x40108BCC	FULL	Memory buffer
CRYPTO_MEM_BUFF756	0x40108BD0	FULL	Memory buffer
CRYPTO_MEM_BUFF757	0x40108BD4	FULL	Memory buffer
CRYPTO_MEM_BUFF758	0x40108BD8	FULL	Memory buffer
CRYPTO_MEM_BUFF759	0x40108BDC	FULL	Memory buffer
CRYPTO_MEM_BUFF760	0x40108BE0	FULL	Memory buffer
CRYPTO_MEM_BUFF761	0x40108BE4	FULL	Memory buffer
CRYPTO_MEM_BUFF762	0x40108BE8	FULL	Memory buffer
CRYPTO_MEM_BUFF763	0x40108BEC	FULL	Memory buffer
CRYPTO_MEM_BUFF764	0x40108BF0	FULL	Memory buffer
CRYPTO_MEM_BUFF765	0x40108BF4	FULL	Memory buffer
CRYPTO_MEM_BUFF766	0x40108BF8	FULL	Memory buffer
CRYPTO_MEM_BUFF767	0x40108BFC	FULL	Memory buffer
CRYPTO_MEM_BUFF768	0x40108C00	FULL	Memory buffer
CRYPTO_MEM_BUFF769	0x40108C04	FULL	Memory buffer
CRYPTO_MEM_BUFF770	0x40108C08	FULL	Memory buffer
CRYPTO_MEM_BUFF771	0x40108C0C	FULL	Memory buffer
CRYPTO_MEM_BUFF772	0x40108C10	FULL	Memory buffer
CRYPTO_MEM_BUFF773	0x40108C14	FULL	Memory buffer
CRYPTO_MEM_BUFF774	0x40108C18	FULL	Memory buffer
CRYPTO_MEM_BUFF775	0x40108C1C	FULL	Memory buffer
CRYPTO_MEM_BUFF776	0x40108C20	FULL	Memory buffer
CRYPTO_MEM_BUFF777	0x40108C24	FULL	Memory buffer
CRYPTO_MEM_BUFF778	0x40108C28	FULL	Memory buffer
CRYPTO_MEM_BUFF779	0x40108C2C	FULL	Memory buffer
CRYPTO_MEM_BUFF780	0x40108C30	FULL	Memory buffer
CRYPTO_MEM_BUFF781	0x40108C34	FULL	Memory buffer
CRYPTO_MEM_BUFF782	0x40108C38	FULL	Memory buffer
CRYPTO_MEM_BUFF783	0x40108C3C	FULL	Memory buffer
CRYPTO_MEM_BUFF784	0x40108C40	FULL	Memory buffer
CRYPTO_MEM_BUFF785	0x40108C44	FULL	Memory buffer
CRYPTO_MEM_BUFF786	0x40108C48	FULL	Memory buffer
CRYPTO_MEM_BUFF787	0x40108C4C	FULL	Memory buffer
CRYPTO_MEM_BUFF788	0x40108C50	FULL	Memory buffer
CRYPTO_MEM_BUFF789	0x40108C54	FULL	Memory buffer
CRYPTO_MEM_BUFF790	0x40108C58	FULL	Memory buffer
CRYPTO_MEM_BUFF791	0x40108C5C	FULL	Memory buffer
CRYPTO_MEM_BUFF792	0x40108C60	FULL	Memory buffer
CRYPTO_MEM_BUFF793	0x40108C64	FULL	Memory buffer
CRYPTO_MEM_BUFF794	0x40108C68	FULL	Memory buffer
CRYPTO_MEM_BUFF795	0x40108C6C	FULL	Memory buffer
CRYPTO_MEM_BUFF796	0x40108C70	FULL	Memory buffer
CRYPTO_MEM_BUFF797	0x40108C74	FULL	Memory buffer
CRYPTO_MEM_BUFF798	0x40108C78	FULL	Memory buffer
CRYPTO_MEM_BUFF799	0x40108C7C	FULL	Memory buffer
CRYPTO_MEM_BUFF800	0x40108C80	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF801	0x40108C84	FULL	Memory buffer
CRYPTO_MEM_BUFF802	0x40108C88	FULL	Memory buffer
CRYPTO_MEM_BUFF803	0x40108C8C	FULL	Memory buffer
CRYPTO_MEM_BUFF804	0x40108C90	FULL	Memory buffer
CRYPTO_MEM_BUFF805	0x40108C94	FULL	Memory buffer
CRYPTO_MEM_BUFF806	0x40108C98	FULL	Memory buffer
CRYPTO_MEM_BUFF807	0x40108C9C	FULL	Memory buffer
CRYPTO_MEM_BUFF808	0x40108CA0	FULL	Memory buffer
CRYPTO_MEM_BUFF809	0x40108CA4	FULL	Memory buffer
CRYPTO_MEM_BUFF810	0x40108CA8	FULL	Memory buffer
CRYPTO_MEM_BUFF811	0x40108CAC	FULL	Memory buffer
CRYPTO_MEM_BUFF812	0x40108CB0	FULL	Memory buffer
CRYPTO_MEM_BUFF813	0x40108CB4	FULL	Memory buffer
CRYPTO_MEM_BUFF814	0x40108CB8	FULL	Memory buffer
CRYPTO_MEM_BUFF815	0x40108CBC	FULL	Memory buffer
CRYPTO_MEM_BUFF816	0x40108CC0	FULL	Memory buffer
CRYPTO_MEM_BUFF817	0x40108CC4	FULL	Memory buffer
CRYPTO_MEM_BUFF818	0x40108CC8	FULL	Memory buffer
CRYPTO_MEM_BUFF819	0x40108CCC	FULL	Memory buffer
CRYPTO_MEM_BUFF820	0x40108CD0	FULL	Memory buffer
CRYPTO_MEM_BUFF821	0x40108CD4	FULL	Memory buffer
CRYPTO_MEM_BUFF822	0x40108CD8	FULL	Memory buffer
CRYPTO_MEM_BUFF823	0x40108CDC	FULL	Memory buffer
CRYPTO_MEM_BUFF824	0x40108CE0	FULL	Memory buffer
CRYPTO_MEM_BUFF825	0x40108CE4	FULL	Memory buffer
CRYPTO_MEM_BUFF826	0x40108CE8	FULL	Memory buffer
CRYPTO_MEM_BUFF827	0x40108CEC	FULL	Memory buffer
CRYPTO_MEM_BUFF828	0x40108CF0	FULL	Memory buffer
CRYPTO_MEM_BUFF829	0x40108CF4	FULL	Memory buffer
CRYPTO_MEM_BUFF830	0x40108CF8	FULL	Memory buffer
CRYPTO_MEM_BUFF831	0x40108CFC	FULL	Memory buffer
CRYPTO_MEM_BUFF832	0x40108D00	FULL	Memory buffer
CRYPTO_MEM_BUFF833	0x40108D04	FULL	Memory buffer
CRYPTO_MEM_BUFF834	0x40108D08	FULL	Memory buffer
CRYPTO_MEM_BUFF835	0x40108D0C	FULL	Memory buffer
CRYPTO_MEM_BUFF836	0x40108D10	FULL	Memory buffer
CRYPTO_MEM_BUFF837	0x40108D14	FULL	Memory buffer
CRYPTO_MEM_BUFF838	0x40108D18	FULL	Memory buffer
CRYPTO_MEM_BUFF839	0x40108D1C	FULL	Memory buffer
CRYPTO_MEM_BUFF840	0x40108D20	FULL	Memory buffer
CRYPTO_MEM_BUFF841	0x40108D24	FULL	Memory buffer
CRYPTO_MEM_BUFF842	0x40108D28	FULL	Memory buffer
CRYPTO_MEM_BUFF843	0x40108D2C	FULL	Memory buffer
CRYPTO_MEM_BUFF844	0x40108D30	FULL	Memory buffer
CRYPTO_MEM_BUFF845	0x40108D34	FULL	Memory buffer
CRYPTO_MEM_BUFF846	0x40108D38	FULL	Memory buffer
CRYPTO_MEM_BUFF847	0x40108D3C	FULL	Memory buffer
CRYPTO_MEM_BUFF848	0x40108D40	FULL	Memory buffer
CRYPTO_MEM_BUFF849	0x40108D44	FULL	Memory buffer
CRYPTO_MEM_BUFF850	0x40108D48	FULL	Memory buffer
CRYPTO_MEM_BUFF851	0x40108D4C	FULL	Memory buffer
CRYPTO_MEM_BUFF852	0x40108D50	FULL	Memory buffer
CRYPTO_MEM_BUFF853	0x40108D54	FULL	Memory buffer
CRYPTO_MEM_BUFF854	0x40108D58	FULL	Memory buffer
CRYPTO_MEM_BUFF855	0x40108D5C	FULL	Memory buffer
CRYPTO_MEM_BUFF856	0x40108D60	FULL	Memory buffer
CRYPTO_MEM_BUFF857	0x40108D64	FULL	Memory buffer
CRYPTO_MEM_BUFF858	0x40108D68	FULL	Memory buffer
CRYPTO_MEM_BUFF859	0x40108D6C	FULL	Memory buffer
CRYPTO_MEM_BUFF860	0x40108D70	FULL	Memory buffer
CRYPTO_MEM_BUFF861	0x40108D74	FULL	Memory buffer
CRYPTO_MEM_BUFF862	0x40108D78	FULL	Memory buffer
CRYPTO_MEM_BUFF863	0x40108D7C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF864	0x40108D80	FULL	Memory buffer
CRYPTO_MEM_BUFF865	0x40108D84	FULL	Memory buffer
CRYPTO_MEM_BUFF866	0x40108D88	FULL	Memory buffer
CRYPTO_MEM_BUFF867	0x40108D8C	FULL	Memory buffer
CRYPTO_MEM_BUFF868	0x40108D90	FULL	Memory buffer
CRYPTO_MEM_BUFF869	0x40108D94	FULL	Memory buffer
CRYPTO_MEM_BUFF870	0x40108D98	FULL	Memory buffer
CRYPTO_MEM_BUFF871	0x40108D9C	FULL	Memory buffer
CRYPTO_MEM_BUFF872	0x40108DA0	FULL	Memory buffer
CRYPTO_MEM_BUFF873	0x40108DA4	FULL	Memory buffer
CRYPTO_MEM_BUFF874	0x40108DA8	FULL	Memory buffer
CRYPTO_MEM_BUFF875	0x40108DAC	FULL	Memory buffer
CRYPTO_MEM_BUFF876	0x40108DB0	FULL	Memory buffer
CRYPTO_MEM_BUFF877	0x40108DB4	FULL	Memory buffer
CRYPTO_MEM_BUFF878	0x40108DB8	FULL	Memory buffer
CRYPTO_MEM_BUFF879	0x40108DBC	FULL	Memory buffer
CRYPTO_MEM_BUFF880	0x40108DC0	FULL	Memory buffer
CRYPTO_MEM_BUFF881	0x40108DC4	FULL	Memory buffer
CRYPTO_MEM_BUFF882	0x40108DC8	FULL	Memory buffer
CRYPTO_MEM_BUFF883	0x40108DCC	FULL	Memory buffer
CRYPTO_MEM_BUFF884	0x40108DD0	FULL	Memory buffer
CRYPTO_MEM_BUFF885	0x40108DD4	FULL	Memory buffer
CRYPTO_MEM_BUFF886	0x40108DD8	FULL	Memory buffer
CRYPTO_MEM_BUFF887	0x40108DDC	FULL	Memory buffer
CRYPTO_MEM_BUFF888	0x40108DE0	FULL	Memory buffer
CRYPTO_MEM_BUFF889	0x40108DE4	FULL	Memory buffer
CRYPTO_MEM_BUFF890	0x40108DE8	FULL	Memory buffer
CRYPTO_MEM_BUFF891	0x40108DEC	FULL	Memory buffer
CRYPTO_MEM_BUFF892	0x40108DF0	FULL	Memory buffer
CRYPTO_MEM_BUFF893	0x40108DF4	FULL	Memory buffer
CRYPTO_MEM_BUFF894	0x40108DF8	FULL	Memory buffer
CRYPTO_MEM_BUFF895	0x40108DFC	FULL	Memory buffer
CRYPTO_MEM_BUFF896	0x40108E00	FULL	Memory buffer
CRYPTO_MEM_BUFF897	0x40108E04	FULL	Memory buffer
CRYPTO_MEM_BUFF898	0x40108E08	FULL	Memory buffer
CRYPTO_MEM_BUFF899	0x40108E0C	FULL	Memory buffer
CRYPTO_MEM_BUFF900	0x40108E10	FULL	Memory buffer
CRYPTO_MEM_BUFF901	0x40108E14	FULL	Memory buffer
CRYPTO_MEM_BUFF902	0x40108E18	FULL	Memory buffer
CRYPTO_MEM_BUFF903	0x40108E1C	FULL	Memory buffer
CRYPTO_MEM_BUFF904	0x40108E20	FULL	Memory buffer
CRYPTO_MEM_BUFF905	0x40108E24	FULL	Memory buffer
CRYPTO_MEM_BUFF906	0x40108E28	FULL	Memory buffer
CRYPTO_MEM_BUFF907	0x40108E2C	FULL	Memory buffer
CRYPTO_MEM_BUFF908	0x40108E30	FULL	Memory buffer
CRYPTO_MEM_BUFF909	0x40108E34	FULL	Memory buffer
CRYPTO_MEM_BUFF910	0x40108E38	FULL	Memory buffer
CRYPTO_MEM_BUFF911	0x40108E3C	FULL	Memory buffer
CRYPTO_MEM_BUFF912	0x40108E40	FULL	Memory buffer
CRYPTO_MEM_BUFF913	0x40108E44	FULL	Memory buffer
CRYPTO_MEM_BUFF914	0x40108E48	FULL	Memory buffer
CRYPTO_MEM_BUFF915	0x40108E4C	FULL	Memory buffer
CRYPTO_MEM_BUFF916	0x40108E50	FULL	Memory buffer
CRYPTO_MEM_BUFF917	0x40108E54	FULL	Memory buffer
CRYPTO_MEM_BUFF918	0x40108E58	FULL	Memory buffer
CRYPTO_MEM_BUFF919	0x40108E5C	FULL	Memory buffer
CRYPTO_MEM_BUFF920	0x40108E60	FULL	Memory buffer
CRYPTO_MEM_BUFF921	0x40108E64	FULL	Memory buffer
CRYPTO_MEM_BUFF922	0x40108E68	FULL	Memory buffer
CRYPTO_MEM_BUFF923	0x40108E6C	FULL	Memory buffer
CRYPTO_MEM_BUFF924	0x40108E70	FULL	Memory buffer
CRYPTO_MEM_BUFF925	0x40108E74	FULL	Memory buffer
CRYPTO_MEM_BUFF926	0x40108E78	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF927	0x40108E7C	FULL	Memory buffer
CRYPTO_MEM_BUFF928	0x40108E80	FULL	Memory buffer
CRYPTO_MEM_BUFF929	0x40108E84	FULL	Memory buffer
CRYPTO_MEM_BUFF930	0x40108E88	FULL	Memory buffer
CRYPTO_MEM_BUFF931	0x40108E8C	FULL	Memory buffer
CRYPTO_MEM_BUFF932	0x40108E90	FULL	Memory buffer
CRYPTO_MEM_BUFF933	0x40108E94	FULL	Memory buffer
CRYPTO_MEM_BUFF934	0x40108E98	FULL	Memory buffer
CRYPTO_MEM_BUFF935	0x40108E9C	FULL	Memory buffer
CRYPTO_MEM_BUFF936	0x40108EA0	FULL	Memory buffer
CRYPTO_MEM_BUFF937	0x40108EA4	FULL	Memory buffer
CRYPTO_MEM_BUFF938	0x40108EA8	FULL	Memory buffer
CRYPTO_MEM_BUFF939	0x40108EAC	FULL	Memory buffer
CRYPTO_MEM_BUFF940	0x40108EB0	FULL	Memory buffer
CRYPTO_MEM_BUFF941	0x40108EB4	FULL	Memory buffer
CRYPTO_MEM_BUFF942	0x40108EB8	FULL	Memory buffer
CRYPTO_MEM_BUFF943	0x40108EBC	FULL	Memory buffer
CRYPTO_MEM_BUFF944	0x40108EC0	FULL	Memory buffer
CRYPTO_MEM_BUFF945	0x40108EC4	FULL	Memory buffer
CRYPTO_MEM_BUFF946	0x40108EC8	FULL	Memory buffer
CRYPTO_MEM_BUFF947	0x40108ECC	FULL	Memory buffer
CRYPTO_MEM_BUFF948	0x40108ED0	FULL	Memory buffer
CRYPTO_MEM_BUFF949	0x40108ED4	FULL	Memory buffer
CRYPTO_MEM_BUFF950	0x40108ED8	FULL	Memory buffer
CRYPTO_MEM_BUFF951	0x40108EDC	FULL	Memory buffer
CRYPTO_MEM_BUFF952	0x40108EE0	FULL	Memory buffer
CRYPTO_MEM_BUFF953	0x40108EE4	FULL	Memory buffer
CRYPTO_MEM_BUFF954	0x40108EE8	FULL	Memory buffer
CRYPTO_MEM_BUFF955	0x40108EEC	FULL	Memory buffer
CRYPTO_MEM_BUFF956	0x40108EF0	FULL	Memory buffer
CRYPTO_MEM_BUFF957	0x40108EF4	FULL	Memory buffer
CRYPTO_MEM_BUFF958	0x40108EF8	FULL	Memory buffer
CRYPTO_MEM_BUFF959	0x40108EFC	FULL	Memory buffer
CRYPTO_MEM_BUFF960	0x40108F00	FULL	Memory buffer
CRYPTO_MEM_BUFF961	0x40108F04	FULL	Memory buffer
CRYPTO_MEM_BUFF962	0x40108F08	FULL	Memory buffer
CRYPTO_MEM_BUFF963	0x40108F0C	FULL	Memory buffer
CRYPTO_MEM_BUFF964	0x40108F10	FULL	Memory buffer
CRYPTO_MEM_BUFF965	0x40108F14	FULL	Memory buffer
CRYPTO_MEM_BUFF966	0x40108F18	FULL	Memory buffer
CRYPTO_MEM_BUFF967	0x40108F1C	FULL	Memory buffer
CRYPTO_MEM_BUFF968	0x40108F20	FULL	Memory buffer
CRYPTO_MEM_BUFF969	0x40108F24	FULL	Memory buffer
CRYPTO_MEM_BUFF970	0x40108F28	FULL	Memory buffer
CRYPTO_MEM_BUFF971	0x40108F2C	FULL	Memory buffer
CRYPTO_MEM_BUFF972	0x40108F30	FULL	Memory buffer
CRYPTO_MEM_BUFF973	0x40108F34	FULL	Memory buffer
CRYPTO_MEM_BUFF974	0x40108F38	FULL	Memory buffer
CRYPTO_MEM_BUFF975	0x40108F3C	FULL	Memory buffer
CRYPTO_MEM_BUFF976	0x40108F40	FULL	Memory buffer
CRYPTO_MEM_BUFF977	0x40108F44	FULL	Memory buffer
CRYPTO_MEM_BUFF978	0x40108F48	FULL	Memory buffer
CRYPTO_MEM_BUFF979	0x40108F4C	FULL	Memory buffer
CRYPTO_MEM_BUFF980	0x40108F50	FULL	Memory buffer
CRYPTO_MEM_BUFF981	0x40108F54	FULL	Memory buffer
CRYPTO_MEM_BUFF982	0x40108F58	FULL	Memory buffer
CRYPTO_MEM_BUFF983	0x40108F5C	FULL	Memory buffer
CRYPTO_MEM_BUFF984	0x40108F60	FULL	Memory buffer
CRYPTO_MEM_BUFF985	0x40108F64	FULL	Memory buffer
CRYPTO_MEM_BUFF986	0x40108F68	FULL	Memory buffer
CRYPTO_MEM_BUFF987	0x40108F6C	FULL	Memory buffer
CRYPTO_MEM_BUFF988	0x40108F70	FULL	Memory buffer
CRYPTO_MEM_BUFF989	0x40108F74	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF990	0x40108F78	FULL	Memory buffer
CRYPTO_MEM_BUFF991	0x40108F7C	FULL	Memory buffer
CRYPTO_MEM_BUFF992	0x40108F80	FULL	Memory buffer
CRYPTO_MEM_BUFF993	0x40108F84	FULL	Memory buffer
CRYPTO_MEM_BUFF994	0x40108F88	FULL	Memory buffer
CRYPTO_MEM_BUFF995	0x40108F8C	FULL	Memory buffer
CRYPTO_MEM_BUFF996	0x40108F90	FULL	Memory buffer
CRYPTO_MEM_BUFF997	0x40108F94	FULL	Memory buffer
CRYPTO_MEM_BUFF998	0x40108F98	FULL	Memory buffer
CRYPTO_MEM_BUFF999	0x40108F9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1000	0x40108FA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1001	0x40108FA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1002	0x40108FA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1003	0x40108FAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1004	0x40108FB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1005	0x40108FB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1006	0x40108FB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1007	0x40108FBC	FULL	Memory buffer
CRYPTO_MEM_BUFF1008	0x40108FC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1009	0x40108FC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1010	0x40108FC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1011	0x40108FCC	FULL	Memory buffer
CRYPTO_MEM_BUFF1012	0x40108FD0	FULL	Memory buffer
CRYPTO_MEM_BUFF1013	0x40108FD4	FULL	Memory buffer
CRYPTO_MEM_BUFF1014	0x40108FD8	FULL	Memory buffer
CRYPTO_MEM_BUFF1015	0x40108FDC	FULL	Memory buffer
CRYPTO_MEM_BUFF1016	0x40108FE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1017	0x40108FE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1018	0x40108FE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1019	0x40108FEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1020	0x40108FF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1021	0x40108FF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1022	0x40108FF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1023	0x40108FFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1024	0x40109000	FULL	Memory buffer
CRYPTO_MEM_BUFF1025	0x40109004	FULL	Memory buffer
CRYPTO_MEM_BUFF1026	0x40109008	FULL	Memory buffer
CRYPTO_MEM_BUFF1027	0x4010900C	FULL	Memory buffer
CRYPTO_MEM_BUFF1028	0x40109010	FULL	Memory buffer
CRYPTO_MEM_BUFF1029	0x40109014	FULL	Memory buffer
CRYPTO_MEM_BUFF1030	0x40109018	FULL	Memory buffer
CRYPTO_MEM_BUFF1031	0x4010901C	FULL	Memory buffer
CRYPTO_MEM_BUFF1032	0x40109020	FULL	Memory buffer
CRYPTO_MEM_BUFF1033	0x40109024	FULL	Memory buffer
CRYPTO_MEM_BUFF1034	0x40109028	FULL	Memory buffer
CRYPTO_MEM_BUFF1035	0x4010902C	FULL	Memory buffer
CRYPTO_MEM_BUFF1036	0x40109030	FULL	Memory buffer
CRYPTO_MEM_BUFF1037	0x40109034	FULL	Memory buffer
CRYPTO_MEM_BUFF1038	0x40109038	FULL	Memory buffer
CRYPTO_MEM_BUFF1039	0x4010903C	FULL	Memory buffer
CRYPTO_MEM_BUFF1040	0x40109040	FULL	Memory buffer
CRYPTO_MEM_BUFF1041	0x40109044	FULL	Memory buffer
CRYPTO_MEM_BUFF1042	0x40109048	FULL	Memory buffer
CRYPTO_MEM_BUFF1043	0x4010904C	FULL	Memory buffer
CRYPTO_MEM_BUFF1044	0x40109050	FULL	Memory buffer
CRYPTO_MEM_BUFF1045	0x40109054	FULL	Memory buffer
CRYPTO_MEM_BUFF1046	0x40109058	FULL	Memory buffer
CRYPTO_MEM_BUFF1047	0x4010905C	FULL	Memory buffer
CRYPTO_MEM_BUFF1048	0x40109060	FULL	Memory buffer
CRYPTO_MEM_BUFF1049	0x40109064	FULL	Memory buffer
CRYPTO_MEM_BUFF1050	0x40109068	FULL	Memory buffer
CRYPTO_MEM_BUFF1051	0x4010906C	FULL	Memory buffer
CRYPTO_MEM_BUFF1052	0x40109070	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1053	0x40109074	FULL	Memory buffer
CRYPTO_MEM_BUFF1054	0x40109078	FULL	Memory buffer
CRYPTO_MEM_BUFF1055	0x4010907C	FULL	Memory buffer
CRYPTO_MEM_BUFF1056	0x40109080	FULL	Memory buffer
CRYPTO_MEM_BUFF1057	0x40109084	FULL	Memory buffer
CRYPTO_MEM_BUFF1058	0x40109088	FULL	Memory buffer
CRYPTO_MEM_BUFF1059	0x4010908C	FULL	Memory buffer
CRYPTO_MEM_BUFF1060	0x40109090	FULL	Memory buffer
CRYPTO_MEM_BUFF1061	0x40109094	FULL	Memory buffer
CRYPTO_MEM_BUFF1062	0x40109098	FULL	Memory buffer
CRYPTO_MEM_BUFF1063	0x4010909C	FULL	Memory buffer
CRYPTO_MEM_BUFF1064	0x401090A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1065	0x401090A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1066	0x401090A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1067	0x401090AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1068	0x401090B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1069	0x401090B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1070	0x401090B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1071	0x401090BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1072	0x401090C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1073	0x401090C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1074	0x401090C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1075	0x401090CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1076	0x401090D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1077	0x401090D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1078	0x401090D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1079	0x401090DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1080	0x401090E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1081	0x401090E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1082	0x401090E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1083	0x401090EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1084	0x401090F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1085	0x401090F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1086	0x401090F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1087	0x401090FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1088	0x40109100	FULL	Memory buffer
CRYPTO_MEM_BUFF1089	0x40109104	FULL	Memory buffer
CRYPTO_MEM_BUFF1090	0x40109108	FULL	Memory buffer
CRYPTO_MEM_BUFF1091	0x4010910C	FULL	Memory buffer
CRYPTO_MEM_BUFF1092	0x40109110	FULL	Memory buffer
CRYPTO_MEM_BUFF1093	0x40109114	FULL	Memory buffer
CRYPTO_MEM_BUFF1094	0x40109118	FULL	Memory buffer
CRYPTO_MEM_BUFF1095	0x4010911C	FULL	Memory buffer
CRYPTO_MEM_BUFF1096	0x40109120	FULL	Memory buffer
CRYPTO_MEM_BUFF1097	0x40109124	FULL	Memory buffer
CRYPTO_MEM_BUFF1098	0x40109128	FULL	Memory buffer
CRYPTO_MEM_BUFF1099	0x4010912C	FULL	Memory buffer
CRYPTO_MEM_BUFF1100	0x40109130	FULL	Memory buffer
CRYPTO_MEM_BUFF1101	0x40109134	FULL	Memory buffer
CRYPTO_MEM_BUFF1102	0x40109138	FULL	Memory buffer
CRYPTO_MEM_BUFF1103	0x4010913C	FULL	Memory buffer
CRYPTO_MEM_BUFF1104	0x40109140	FULL	Memory buffer
CRYPTO_MEM_BUFF1105	0x40109144	FULL	Memory buffer
CRYPTO_MEM_BUFF1106	0x40109148	FULL	Memory buffer
CRYPTO_MEM_BUFF1107	0x4010914C	FULL	Memory buffer
CRYPTO_MEM_BUFF1108	0x40109150	FULL	Memory buffer
CRYPTO_MEM_BUFF1109	0x40109154	FULL	Memory buffer
CRYPTO_MEM_BUFF1110	0x40109158	FULL	Memory buffer
CRYPTO_MEM_BUFF1111	0x4010915C	FULL	Memory buffer
CRYPTO_MEM_BUFF1112	0x40109160	FULL	Memory buffer
CRYPTO_MEM_BUFF1113	0x40109164	FULL	Memory buffer
CRYPTO_MEM_BUFF1114	0x40109168	FULL	Memory buffer
CRYPTO_MEM_BUFF1115	0x4010916C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1116	0x40109170	FULL	Memory buffer
CRYPTO_MEM_BUFF1117	0x40109174	FULL	Memory buffer
CRYPTO_MEM_BUFF1118	0x40109178	FULL	Memory buffer
CRYPTO_MEM_BUFF1119	0x4010917C	FULL	Memory buffer
CRYPTO_MEM_BUFF1120	0x40109180	FULL	Memory buffer
CRYPTO_MEM_BUFF1121	0x40109184	FULL	Memory buffer
CRYPTO_MEM_BUFF1122	0x40109188	FULL	Memory buffer
CRYPTO_MEM_BUFF1123	0x4010918C	FULL	Memory buffer
CRYPTO_MEM_BUFF1124	0x40109190	FULL	Memory buffer
CRYPTO_MEM_BUFF1125	0x40109194	FULL	Memory buffer
CRYPTO_MEM_BUFF1126	0x40109198	FULL	Memory buffer
CRYPTO_MEM_BUFF1127	0x4010919C	FULL	Memory buffer
CRYPTO_MEM_BUFF1128	0x401091A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1129	0x401091A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1130	0x401091A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1131	0x401091AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1132	0x401091B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1133	0x401091B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1134	0x401091B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1135	0x401091BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1136	0x401091C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1137	0x401091C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1138	0x401091C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1139	0x401091CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1140	0x401091D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1141	0x401091D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1142	0x401091D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1143	0x401091DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1144	0x401091E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1145	0x401091E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1146	0x401091E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1147	0x401091EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1148	0x401091F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1149	0x401091F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1150	0x401091F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1151	0x401091FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1152	0x40109200	FULL	Memory buffer
CRYPTO_MEM_BUFF1153	0x40109204	FULL	Memory buffer
CRYPTO_MEM_BUFF1154	0x40109208	FULL	Memory buffer
CRYPTO_MEM_BUFF1155	0x4010920C	FULL	Memory buffer
CRYPTO_MEM_BUFF1156	0x40109210	FULL	Memory buffer
CRYPTO_MEM_BUFF1157	0x40109214	FULL	Memory buffer
CRYPTO_MEM_BUFF1158	0x40109218	FULL	Memory buffer
CRYPTO_MEM_BUFF1159	0x4010921C	FULL	Memory buffer
CRYPTO_MEM_BUFF1160	0x40109220	FULL	Memory buffer
CRYPTO_MEM_BUFF1161	0x40109224	FULL	Memory buffer
CRYPTO_MEM_BUFF1162	0x40109228	FULL	Memory buffer
CRYPTO_MEM_BUFF1163	0x4010922C	FULL	Memory buffer
CRYPTO_MEM_BUFF1164	0x40109230	FULL	Memory buffer
CRYPTO_MEM_BUFF1165	0x40109234	FULL	Memory buffer
CRYPTO_MEM_BUFF1166	0x40109238	FULL	Memory buffer
CRYPTO_MEM_BUFF1167	0x4010923C	FULL	Memory buffer
CRYPTO_MEM_BUFF1168	0x40109240	FULL	Memory buffer
CRYPTO_MEM_BUFF1169	0x40109244	FULL	Memory buffer
CRYPTO_MEM_BUFF1170	0x40109248	FULL	Memory buffer
CRYPTO_MEM_BUFF1171	0x4010924C	FULL	Memory buffer
CRYPTO_MEM_BUFF1172	0x40109250	FULL	Memory buffer
CRYPTO_MEM_BUFF1173	0x40109254	FULL	Memory buffer
CRYPTO_MEM_BUFF1174	0x40109258	FULL	Memory buffer
CRYPTO_MEM_BUFF1175	0x4010925C	FULL	Memory buffer
CRYPTO_MEM_BUFF1176	0x40109260	FULL	Memory buffer
CRYPTO_MEM_BUFF1177	0x40109264	FULL	Memory buffer
CRYPTO_MEM_BUFF1178	0x40109268	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1179	0x4010926C	FULL	Memory buffer
CRYPTO_MEM_BUFF1180	0x40109270	FULL	Memory buffer
CRYPTO_MEM_BUFF1181	0x40109274	FULL	Memory buffer
CRYPTO_MEM_BUFF1182	0x40109278	FULL	Memory buffer
CRYPTO_MEM_BUFF1183	0x4010927C	FULL	Memory buffer
CRYPTO_MEM_BUFF1184	0x40109280	FULL	Memory buffer
CRYPTO_MEM_BUFF1185	0x40109284	FULL	Memory buffer
CRYPTO_MEM_BUFF1186	0x40109288	FULL	Memory buffer
CRYPTO_MEM_BUFF1187	0x4010928C	FULL	Memory buffer
CRYPTO_MEM_BUFF1188	0x40109290	FULL	Memory buffer
CRYPTO_MEM_BUFF1189	0x40109294	FULL	Memory buffer
CRYPTO_MEM_BUFF1190	0x40109298	FULL	Memory buffer
CRYPTO_MEM_BUFF1191	0x4010929C	FULL	Memory buffer
CRYPTO_MEM_BUFF1192	0x401092A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1193	0x401092A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1194	0x401092A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1195	0x401092AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1196	0x401092B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1197	0x401092B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1198	0x401092B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1199	0x401092BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1200	0x401092C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1201	0x401092C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1202	0x401092C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1203	0x401092CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1204	0x401092D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1205	0x401092D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1206	0x401092D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1207	0x401092DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1208	0x401092E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1209	0x401092E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1210	0x401092E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1211	0x401092EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1212	0x401092F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1213	0x401092F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1214	0x401092F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1215	0x401092FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1216	0x40109300	FULL	Memory buffer
CRYPTO_MEM_BUFF1217	0x40109304	FULL	Memory buffer
CRYPTO_MEM_BUFF1218	0x40109308	FULL	Memory buffer
CRYPTO_MEM_BUFF1219	0x4010930C	FULL	Memory buffer
CRYPTO_MEM_BUFF1220	0x40109310	FULL	Memory buffer
CRYPTO_MEM_BUFF1221	0x40109314	FULL	Memory buffer
CRYPTO_MEM_BUFF1222	0x40109318	FULL	Memory buffer
CRYPTO_MEM_BUFF1223	0x4010931C	FULL	Memory buffer
CRYPTO_MEM_BUFF1224	0x40109320	FULL	Memory buffer
CRYPTO_MEM_BUFF1225	0x40109324	FULL	Memory buffer
CRYPTO_MEM_BUFF1226	0x40109328	FULL	Memory buffer
CRYPTO_MEM_BUFF1227	0x4010932C	FULL	Memory buffer
CRYPTO_MEM_BUFF1228	0x40109330	FULL	Memory buffer
CRYPTO_MEM_BUFF1229	0x40109334	FULL	Memory buffer
CRYPTO_MEM_BUFF1230	0x40109338	FULL	Memory buffer
CRYPTO_MEM_BUFF1231	0x4010933C	FULL	Memory buffer
CRYPTO_MEM_BUFF1232	0x40109340	FULL	Memory buffer
CRYPTO_MEM_BUFF1233	0x40109344	FULL	Memory buffer
CRYPTO_MEM_BUFF1234	0x40109348	FULL	Memory buffer
CRYPTO_MEM_BUFF1235	0x4010934C	FULL	Memory buffer
CRYPTO_MEM_BUFF1236	0x40109350	FULL	Memory buffer
CRYPTO_MEM_BUFF1237	0x40109354	FULL	Memory buffer
CRYPTO_MEM_BUFF1238	0x40109358	FULL	Memory buffer
CRYPTO_MEM_BUFF1239	0x4010935C	FULL	Memory buffer
CRYPTO_MEM_BUFF1240	0x40109360	FULL	Memory buffer
CRYPTO_MEM_BUFF1241	0x40109364	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1242	0x40109368	FULL	Memory buffer
CRYPTO_MEM_BUFF1243	0x4010936C	FULL	Memory buffer
CRYPTO_MEM_BUFF1244	0x40109370	FULL	Memory buffer
CRYPTO_MEM_BUFF1245	0x40109374	FULL	Memory buffer
CRYPTO_MEM_BUFF1246	0x40109378	FULL	Memory buffer
CRYPTO_MEM_BUFF1247	0x4010937C	FULL	Memory buffer
CRYPTO_MEM_BUFF1248	0x40109380	FULL	Memory buffer
CRYPTO_MEM_BUFF1249	0x40109384	FULL	Memory buffer
CRYPTO_MEM_BUFF1250	0x40109388	FULL	Memory buffer
CRYPTO_MEM_BUFF1251	0x4010938C	FULL	Memory buffer
CRYPTO_MEM_BUFF1252	0x40109390	FULL	Memory buffer
CRYPTO_MEM_BUFF1253	0x40109394	FULL	Memory buffer
CRYPTO_MEM_BUFF1254	0x40109398	FULL	Memory buffer
CRYPTO_MEM_BUFF1255	0x4010939C	FULL	Memory buffer
CRYPTO_MEM_BUFF1256	0x401093A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1257	0x401093A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1258	0x401093A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1259	0x401093AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1260	0x401093B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1261	0x401093B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1262	0x401093B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1263	0x401093BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1264	0x401093C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1265	0x401093C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1266	0x401093C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1267	0x401093CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1268	0x401093D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1269	0x401093D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1270	0x401093D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1271	0x401093DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1272	0x401093E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1273	0x401093E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1274	0x401093E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1275	0x401093EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1276	0x401093F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1277	0x401093F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1278	0x401093F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1279	0x401093FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1280	0x40109400	FULL	Memory buffer
CRYPTO_MEM_BUFF1281	0x40109404	FULL	Memory buffer
CRYPTO_MEM_BUFF1282	0x40109408	FULL	Memory buffer
CRYPTO_MEM_BUFF1283	0x4010940C	FULL	Memory buffer
CRYPTO_MEM_BUFF1284	0x40109410	FULL	Memory buffer
CRYPTO_MEM_BUFF1285	0x40109414	FULL	Memory buffer
CRYPTO_MEM_BUFF1286	0x40109418	FULL	Memory buffer
CRYPTO_MEM_BUFF1287	0x4010941C	FULL	Memory buffer
CRYPTO_MEM_BUFF1288	0x40109420	FULL	Memory buffer
CRYPTO_MEM_BUFF1289	0x40109424	FULL	Memory buffer
CRYPTO_MEM_BUFF1290	0x40109428	FULL	Memory buffer
CRYPTO_MEM_BUFF1291	0x4010942C	FULL	Memory buffer
CRYPTO_MEM_BUFF1292	0x40109430	FULL	Memory buffer
CRYPTO_MEM_BUFF1293	0x40109434	FULL	Memory buffer
CRYPTO_MEM_BUFF1294	0x40109438	FULL	Memory buffer
CRYPTO_MEM_BUFF1295	0x4010943C	FULL	Memory buffer
CRYPTO_MEM_BUFF1296	0x40109440	FULL	Memory buffer
CRYPTO_MEM_BUFF1297	0x40109444	FULL	Memory buffer
CRYPTO_MEM_BUFF1298	0x40109448	FULL	Memory buffer
CRYPTO_MEM_BUFF1299	0x4010944C	FULL	Memory buffer
CRYPTO_MEM_BUFF1300	0x40109450	FULL	Memory buffer
CRYPTO_MEM_BUFF1301	0x40109454	FULL	Memory buffer
CRYPTO_MEM_BUFF1302	0x40109458	FULL	Memory buffer
CRYPTO_MEM_BUFF1303	0x4010945C	FULL	Memory buffer
CRYPTO_MEM_BUFF1304	0x40109460	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1305	0x40109464	FULL	Memory buffer
CRYPTO_MEM_BUFF1306	0x40109468	FULL	Memory buffer
CRYPTO_MEM_BUFF1307	0x4010946C	FULL	Memory buffer
CRYPTO_MEM_BUFF1308	0x40109470	FULL	Memory buffer
CRYPTO_MEM_BUFF1309	0x40109474	FULL	Memory buffer
CRYPTO_MEM_BUFF1310	0x40109478	FULL	Memory buffer
CRYPTO_MEM_BUFF1311	0x4010947C	FULL	Memory buffer
CRYPTO_MEM_BUFF1312	0x40109480	FULL	Memory buffer
CRYPTO_MEM_BUFF1313	0x40109484	FULL	Memory buffer
CRYPTO_MEM_BUFF1314	0x40109488	FULL	Memory buffer
CRYPTO_MEM_BUFF1315	0x4010948C	FULL	Memory buffer
CRYPTO_MEM_BUFF1316	0x40109490	FULL	Memory buffer
CRYPTO_MEM_BUFF1317	0x40109494	FULL	Memory buffer
CRYPTO_MEM_BUFF1318	0x40109498	FULL	Memory buffer
CRYPTO_MEM_BUFF1319	0x4010949C	FULL	Memory buffer
CRYPTO_MEM_BUFF1320	0x401094A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1321	0x401094A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1322	0x401094A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1323	0x401094AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1324	0x401094B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1325	0x401094B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1326	0x401094B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1327	0x401094BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1328	0x401094C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1329	0x401094C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1330	0x401094C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1331	0x401094CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1332	0x401094D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1333	0x401094D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1334	0x401094D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1335	0x401094DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1336	0x401094E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1337	0x401094E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1338	0x401094E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1339	0x401094EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1340	0x401094F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1341	0x401094F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1342	0x401094F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1343	0x401094FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1344	0x40109500	FULL	Memory buffer
CRYPTO_MEM_BUFF1345	0x40109504	FULL	Memory buffer
CRYPTO_MEM_BUFF1346	0x40109508	FULL	Memory buffer
CRYPTO_MEM_BUFF1347	0x4010950C	FULL	Memory buffer
CRYPTO_MEM_BUFF1348	0x40109510	FULL	Memory buffer
CRYPTO_MEM_BUFF1349	0x40109514	FULL	Memory buffer
CRYPTO_MEM_BUFF1350	0x40109518	FULL	Memory buffer
CRYPTO_MEM_BUFF1351	0x4010951C	FULL	Memory buffer
CRYPTO_MEM_BUFF1352	0x40109520	FULL	Memory buffer
CRYPTO_MEM_BUFF1353	0x40109524	FULL	Memory buffer
CRYPTO_MEM_BUFF1354	0x40109528	FULL	Memory buffer
CRYPTO_MEM_BUFF1355	0x4010952C	FULL	Memory buffer
CRYPTO_MEM_BUFF1356	0x40109530	FULL	Memory buffer
CRYPTO_MEM_BUFF1357	0x40109534	FULL	Memory buffer
CRYPTO_MEM_BUFF1358	0x40109538	FULL	Memory buffer
CRYPTO_MEM_BUFF1359	0x4010953C	FULL	Memory buffer
CRYPTO_MEM_BUFF1360	0x40109540	FULL	Memory buffer
CRYPTO_MEM_BUFF1361	0x40109544	FULL	Memory buffer
CRYPTO_MEM_BUFF1362	0x40109548	FULL	Memory buffer
CRYPTO_MEM_BUFF1363	0x4010954C	FULL	Memory buffer
CRYPTO_MEM_BUFF1364	0x40109550	FULL	Memory buffer
CRYPTO_MEM_BUFF1365	0x40109554	FULL	Memory buffer
CRYPTO_MEM_BUFF1366	0x40109558	FULL	Memory buffer
CRYPTO_MEM_BUFF1367	0x4010955C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1368	0x40109560	FULL	Memory buffer
CRYPTO_MEM_BUFF1369	0x40109564	FULL	Memory buffer
CRYPTO_MEM_BUFF1370	0x40109568	FULL	Memory buffer
CRYPTO_MEM_BUFF1371	0x4010956C	FULL	Memory buffer
CRYPTO_MEM_BUFF1372	0x40109570	FULL	Memory buffer
CRYPTO_MEM_BUFF1373	0x40109574	FULL	Memory buffer
CRYPTO_MEM_BUFF1374	0x40109578	FULL	Memory buffer
CRYPTO_MEM_BUFF1375	0x4010957C	FULL	Memory buffer
CRYPTO_MEM_BUFF1376	0x40109580	FULL	Memory buffer
CRYPTO_MEM_BUFF1377	0x40109584	FULL	Memory buffer
CRYPTO_MEM_BUFF1378	0x40109588	FULL	Memory buffer
CRYPTO_MEM_BUFF1379	0x4010958C	FULL	Memory buffer
CRYPTO_MEM_BUFF1380	0x40109590	FULL	Memory buffer
CRYPTO_MEM_BUFF1381	0x40109594	FULL	Memory buffer
CRYPTO_MEM_BUFF1382	0x40109598	FULL	Memory buffer
CRYPTO_MEM_BUFF1383	0x4010959C	FULL	Memory buffer
CRYPTO_MEM_BUFF1384	0x401095A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1385	0x401095A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1386	0x401095A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1387	0x401095AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1388	0x401095B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1389	0x401095B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1390	0x401095B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1391	0x401095BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1392	0x401095C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1393	0x401095C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1394	0x401095C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1395	0x401095CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1396	0x401095D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1397	0x401095D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1398	0x401095D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1399	0x401095DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1400	0x401095E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1401	0x401095E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1402	0x401095E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1403	0x401095EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1404	0x401095F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1405	0x401095F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1406	0x401095F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1407	0x401095FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1408	0x40109600	FULL	Memory buffer
CRYPTO_MEM_BUFF1409	0x40109604	FULL	Memory buffer
CRYPTO_MEM_BUFF1410	0x40109608	FULL	Memory buffer
CRYPTO_MEM_BUFF1411	0x4010960C	FULL	Memory buffer
CRYPTO_MEM_BUFF1412	0x40109610	FULL	Memory buffer
CRYPTO_MEM_BUFF1413	0x40109614	FULL	Memory buffer
CRYPTO_MEM_BUFF1414	0x40109618	FULL	Memory buffer
CRYPTO_MEM_BUFF1415	0x4010961C	FULL	Memory buffer
CRYPTO_MEM_BUFF1416	0x40109620	FULL	Memory buffer
CRYPTO_MEM_BUFF1417	0x40109624	FULL	Memory buffer
CRYPTO_MEM_BUFF1418	0x40109628	FULL	Memory buffer
CRYPTO_MEM_BUFF1419	0x4010962C	FULL	Memory buffer
CRYPTO_MEM_BUFF1420	0x40109630	FULL	Memory buffer
CRYPTO_MEM_BUFF1421	0x40109634	FULL	Memory buffer
CRYPTO_MEM_BUFF1422	0x40109638	FULL	Memory buffer
CRYPTO_MEM_BUFF1423	0x4010963C	FULL	Memory buffer
CRYPTO_MEM_BUFF1424	0x40109640	FULL	Memory buffer
CRYPTO_MEM_BUFF1425	0x40109644	FULL	Memory buffer
CRYPTO_MEM_BUFF1426	0x40109648	FULL	Memory buffer
CRYPTO_MEM_BUFF1427	0x4010964C	FULL	Memory buffer
CRYPTO_MEM_BUFF1428	0x40109650	FULL	Memory buffer
CRYPTO_MEM_BUFF1429	0x40109654	FULL	Memory buffer
CRYPTO_MEM_BUFF1430	0x40109658	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1431	0x4010965C	FULL	Memory buffer
CRYPTO_MEM_BUFF1432	0x40109660	FULL	Memory buffer
CRYPTO_MEM_BUFF1433	0x40109664	FULL	Memory buffer
CRYPTO_MEM_BUFF1434	0x40109668	FULL	Memory buffer
CRYPTO_MEM_BUFF1435	0x4010966C	FULL	Memory buffer
CRYPTO_MEM_BUFF1436	0x40109670	FULL	Memory buffer
CRYPTO_MEM_BUFF1437	0x40109674	FULL	Memory buffer
CRYPTO_MEM_BUFF1438	0x40109678	FULL	Memory buffer
CRYPTO_MEM_BUFF1439	0x4010967C	FULL	Memory buffer
CRYPTO_MEM_BUFF1440	0x40109680	FULL	Memory buffer
CRYPTO_MEM_BUFF1441	0x40109684	FULL	Memory buffer
CRYPTO_MEM_BUFF1442	0x40109688	FULL	Memory buffer
CRYPTO_MEM_BUFF1443	0x4010968C	FULL	Memory buffer
CRYPTO_MEM_BUFF1444	0x40109690	FULL	Memory buffer
CRYPTO_MEM_BUFF1445	0x40109694	FULL	Memory buffer
CRYPTO_MEM_BUFF1446	0x40109698	FULL	Memory buffer
CRYPTO_MEM_BUFF1447	0x4010969C	FULL	Memory buffer
CRYPTO_MEM_BUFF1448	0x401096A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1449	0x401096A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1450	0x401096A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1451	0x401096AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1452	0x401096B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1453	0x401096B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1454	0x401096B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1455	0x401096BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1456	0x401096C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1457	0x401096C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1458	0x401096C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1459	0x401096CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1460	0x401096D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1461	0x401096D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1462	0x401096D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1463	0x401096DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1464	0x401096E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1465	0x401096E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1466	0x401096E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1467	0x401096EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1468	0x401096F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1469	0x401096F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1470	0x401096F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1471	0x401096FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1472	0x40109700	FULL	Memory buffer
CRYPTO_MEM_BUFF1473	0x40109704	FULL	Memory buffer
CRYPTO_MEM_BUFF1474	0x40109708	FULL	Memory buffer
CRYPTO_MEM_BUFF1475	0x4010970C	FULL	Memory buffer
CRYPTO_MEM_BUFF1476	0x40109710	FULL	Memory buffer
CRYPTO_MEM_BUFF1477	0x40109714	FULL	Memory buffer
CRYPTO_MEM_BUFF1478	0x40109718	FULL	Memory buffer
CRYPTO_MEM_BUFF1479	0x4010971C	FULL	Memory buffer
CRYPTO_MEM_BUFF1480	0x40109720	FULL	Memory buffer
CRYPTO_MEM_BUFF1481	0x40109724	FULL	Memory buffer
CRYPTO_MEM_BUFF1482	0x40109728	FULL	Memory buffer
CRYPTO_MEM_BUFF1483	0x4010972C	FULL	Memory buffer
CRYPTO_MEM_BUFF1484	0x40109730	FULL	Memory buffer
CRYPTO_MEM_BUFF1485	0x40109734	FULL	Memory buffer
CRYPTO_MEM_BUFF1486	0x40109738	FULL	Memory buffer
CRYPTO_MEM_BUFF1487	0x4010973C	FULL	Memory buffer
CRYPTO_MEM_BUFF1488	0x40109740	FULL	Memory buffer
CRYPTO_MEM_BUFF1489	0x40109744	FULL	Memory buffer
CRYPTO_MEM_BUFF1490	0x40109748	FULL	Memory buffer
CRYPTO_MEM_BUFF1491	0x4010974C	FULL	Memory buffer
CRYPTO_MEM_BUFF1492	0x40109750	FULL	Memory buffer
CRYPTO_MEM_BUFF1493	0x40109754	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1494	0x40109758	FULL	Memory buffer
CRYPTO_MEM_BUFF1495	0x4010975C	FULL	Memory buffer
CRYPTO_MEM_BUFF1496	0x40109760	FULL	Memory buffer
CRYPTO_MEM_BUFF1497	0x40109764	FULL	Memory buffer
CRYPTO_MEM_BUFF1498	0x40109768	FULL	Memory buffer
CRYPTO_MEM_BUFF1499	0x4010976C	FULL	Memory buffer
CRYPTO_MEM_BUFF1500	0x40109770	FULL	Memory buffer
CRYPTO_MEM_BUFF1501	0x40109774	FULL	Memory buffer
CRYPTO_MEM_BUFF1502	0x40109778	FULL	Memory buffer
CRYPTO_MEM_BUFF1503	0x4010977C	FULL	Memory buffer
CRYPTO_MEM_BUFF1504	0x40109780	FULL	Memory buffer
CRYPTO_MEM_BUFF1505	0x40109784	FULL	Memory buffer
CRYPTO_MEM_BUFF1506	0x40109788	FULL	Memory buffer
CRYPTO_MEM_BUFF1507	0x4010978C	FULL	Memory buffer
CRYPTO_MEM_BUFF1508	0x40109790	FULL	Memory buffer
CRYPTO_MEM_BUFF1509	0x40109794	FULL	Memory buffer
CRYPTO_MEM_BUFF1510	0x40109798	FULL	Memory buffer
CRYPTO_MEM_BUFF1511	0x4010979C	FULL	Memory buffer
CRYPTO_MEM_BUFF1512	0x401097A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1513	0x401097A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1514	0x401097A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1515	0x401097AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1516	0x401097B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1517	0x401097B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1518	0x401097B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1519	0x401097BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1520	0x401097C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1521	0x401097C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1522	0x401097C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1523	0x401097CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1524	0x401097D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1525	0x401097D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1526	0x401097D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1527	0x401097DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1528	0x401097E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1529	0x401097E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1530	0x401097E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1531	0x401097EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1532	0x401097F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1533	0x401097F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1534	0x401097F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1535	0x401097FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1536	0x40109800	FULL	Memory buffer
CRYPTO_MEM_BUFF1537	0x40109804	FULL	Memory buffer
CRYPTO_MEM_BUFF1538	0x40109808	FULL	Memory buffer
CRYPTO_MEM_BUFF1539	0x4010980C	FULL	Memory buffer
CRYPTO_MEM_BUFF1540	0x40109810	FULL	Memory buffer
CRYPTO_MEM_BUFF1541	0x40109814	FULL	Memory buffer
CRYPTO_MEM_BUFF1542	0x40109818	FULL	Memory buffer
CRYPTO_MEM_BUFF1543	0x4010981C	FULL	Memory buffer
CRYPTO_MEM_BUFF1544	0x40109820	FULL	Memory buffer
CRYPTO_MEM_BUFF1545	0x40109824	FULL	Memory buffer
CRYPTO_MEM_BUFF1546	0x40109828	FULL	Memory buffer
CRYPTO_MEM_BUFF1547	0x4010982C	FULL	Memory buffer
CRYPTO_MEM_BUFF1548	0x40109830	FULL	Memory buffer
CRYPTO_MEM_BUFF1549	0x40109834	FULL	Memory buffer
CRYPTO_MEM_BUFF1550	0x40109838	FULL	Memory buffer
CRYPTO_MEM_BUFF1551	0x4010983C	FULL	Memory buffer
CRYPTO_MEM_BUFF1552	0x40109840	FULL	Memory buffer
CRYPTO_MEM_BUFF1553	0x40109844	FULL	Memory buffer
CRYPTO_MEM_BUFF1554	0x40109848	FULL	Memory buffer
CRYPTO_MEM_BUFF1555	0x4010984C	FULL	Memory buffer
CRYPTO_MEM_BUFF1556	0x40109850	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1557	0x40109854	FULL	Memory buffer
CRYPTO_MEM_BUFF1558	0x40109858	FULL	Memory buffer
CRYPTO_MEM_BUFF1559	0x4010985C	FULL	Memory buffer
CRYPTO_MEM_BUFF1560	0x40109860	FULL	Memory buffer
CRYPTO_MEM_BUFF1561	0x40109864	FULL	Memory buffer
CRYPTO_MEM_BUFF1562	0x40109868	FULL	Memory buffer
CRYPTO_MEM_BUFF1563	0x4010986C	FULL	Memory buffer
CRYPTO_MEM_BUFF1564	0x40109870	FULL	Memory buffer
CRYPTO_MEM_BUFF1565	0x40109874	FULL	Memory buffer
CRYPTO_MEM_BUFF1566	0x40109878	FULL	Memory buffer
CRYPTO_MEM_BUFF1567	0x4010987C	FULL	Memory buffer
CRYPTO_MEM_BUFF1568	0x40109880	FULL	Memory buffer
CRYPTO_MEM_BUFF1569	0x40109884	FULL	Memory buffer
CRYPTO_MEM_BUFF1570	0x40109888	FULL	Memory buffer
CRYPTO_MEM_BUFF1571	0x4010988C	FULL	Memory buffer
CRYPTO_MEM_BUFF1572	0x40109890	FULL	Memory buffer
CRYPTO_MEM_BUFF1573	0x40109894	FULL	Memory buffer
CRYPTO_MEM_BUFF1574	0x40109898	FULL	Memory buffer
CRYPTO_MEM_BUFF1575	0x4010989C	FULL	Memory buffer
CRYPTO_MEM_BUFF1576	0x401098A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1577	0x401098A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1578	0x401098A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1579	0x401098AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1580	0x401098B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1581	0x401098B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1582	0x401098B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1583	0x401098BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1584	0x401098C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1585	0x401098C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1586	0x401098C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1587	0x401098CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1588	0x401098D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1589	0x401098D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1590	0x401098D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1591	0x401098DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1592	0x401098E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1593	0x401098E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1594	0x401098E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1595	0x401098EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1596	0x401098F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1597	0x401098F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1598	0x401098F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1599	0x401098FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1600	0x40109900	FULL	Memory buffer
CRYPTO_MEM_BUFF1601	0x40109904	FULL	Memory buffer
CRYPTO_MEM_BUFF1602	0x40109908	FULL	Memory buffer
CRYPTO_MEM_BUFF1603	0x4010990C	FULL	Memory buffer
CRYPTO_MEM_BUFF1604	0x40109910	FULL	Memory buffer
CRYPTO_MEM_BUFF1605	0x40109914	FULL	Memory buffer
CRYPTO_MEM_BUFF1606	0x40109918	FULL	Memory buffer
CRYPTO_MEM_BUFF1607	0x4010991C	FULL	Memory buffer
CRYPTO_MEM_BUFF1608	0x40109920	FULL	Memory buffer
CRYPTO_MEM_BUFF1609	0x40109924	FULL	Memory buffer
CRYPTO_MEM_BUFF1610	0x40109928	FULL	Memory buffer
CRYPTO_MEM_BUFF1611	0x4010992C	FULL	Memory buffer
CRYPTO_MEM_BUFF1612	0x40109930	FULL	Memory buffer
CRYPTO_MEM_BUFF1613	0x40109934	FULL	Memory buffer
CRYPTO_MEM_BUFF1614	0x40109938	FULL	Memory buffer
CRYPTO_MEM_BUFF1615	0x4010993C	FULL	Memory buffer
CRYPTO_MEM_BUFF1616	0x40109940	FULL	Memory buffer
CRYPTO_MEM_BUFF1617	0x40109944	FULL	Memory buffer
CRYPTO_MEM_BUFF1618	0x40109948	FULL	Memory buffer
CRYPTO_MEM_BUFF1619	0x4010994C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1620	0x40109950	FULL	Memory buffer
CRYPTO_MEM_BUFF1621	0x40109954	FULL	Memory buffer
CRYPTO_MEM_BUFF1622	0x40109958	FULL	Memory buffer
CRYPTO_MEM_BUFF1623	0x4010995C	FULL	Memory buffer
CRYPTO_MEM_BUFF1624	0x40109960	FULL	Memory buffer
CRYPTO_MEM_BUFF1625	0x40109964	FULL	Memory buffer
CRYPTO_MEM_BUFF1626	0x40109968	FULL	Memory buffer
CRYPTO_MEM_BUFF1627	0x4010996C	FULL	Memory buffer
CRYPTO_MEM_BUFF1628	0x40109970	FULL	Memory buffer
CRYPTO_MEM_BUFF1629	0x40109974	FULL	Memory buffer
CRYPTO_MEM_BUFF1630	0x40109978	FULL	Memory buffer
CRYPTO_MEM_BUFF1631	0x4010997C	FULL	Memory buffer
CRYPTO_MEM_BUFF1632	0x40109980	FULL	Memory buffer
CRYPTO_MEM_BUFF1633	0x40109984	FULL	Memory buffer
CRYPTO_MEM_BUFF1634	0x40109988	FULL	Memory buffer
CRYPTO_MEM_BUFF1635	0x4010998C	FULL	Memory buffer
CRYPTO_MEM_BUFF1636	0x40109990	FULL	Memory buffer
CRYPTO_MEM_BUFF1637	0x40109994	FULL	Memory buffer
CRYPTO_MEM_BUFF1638	0x40109998	FULL	Memory buffer
CRYPTO_MEM_BUFF1639	0x4010999C	FULL	Memory buffer
CRYPTO_MEM_BUFF1640	0x401099A0	FULL	Memory buffer
CRYPTO_MEM_BUFF1641	0x401099A4	FULL	Memory buffer
CRYPTO_MEM_BUFF1642	0x401099A8	FULL	Memory buffer
CRYPTO_MEM_BUFF1643	0x401099AC	FULL	Memory buffer
CRYPTO_MEM_BUFF1644	0x401099B0	FULL	Memory buffer
CRYPTO_MEM_BUFF1645	0x401099B4	FULL	Memory buffer
CRYPTO_MEM_BUFF1646	0x401099B8	FULL	Memory buffer
CRYPTO_MEM_BUFF1647	0x401099BC	FULL	Memory buffer
CRYPTO_MEM_BUFF1648	0x401099C0	FULL	Memory buffer
CRYPTO_MEM_BUFF1649	0x401099C4	FULL	Memory buffer
CRYPTO_MEM_BUFF1650	0x401099C8	FULL	Memory buffer
CRYPTO_MEM_BUFF1651	0x401099CC	FULL	Memory buffer
CRYPTO_MEM_BUFF1652	0x401099D0	FULL	Memory buffer
CRYPTO_MEM_BUFF1653	0x401099D4	FULL	Memory buffer
CRYPTO_MEM_BUFF1654	0x401099D8	FULL	Memory buffer
CRYPTO_MEM_BUFF1655	0x401099DC	FULL	Memory buffer
CRYPTO_MEM_BUFF1656	0x401099E0	FULL	Memory buffer
CRYPTO_MEM_BUFF1657	0x401099E4	FULL	Memory buffer
CRYPTO_MEM_BUFF1658	0x401099E8	FULL	Memory buffer
CRYPTO_MEM_BUFF1659	0x401099EC	FULL	Memory buffer
CRYPTO_MEM_BUFF1660	0x401099F0	FULL	Memory buffer
CRYPTO_MEM_BUFF1661	0x401099F4	FULL	Memory buffer
CRYPTO_MEM_BUFF1662	0x401099F8	FULL	Memory buffer
CRYPTO_MEM_BUFF1663	0x401099FC	FULL	Memory buffer
CRYPTO_MEM_BUFF1664	0x40109A00	FULL	Memory buffer
CRYPTO_MEM_BUFF1665	0x40109A04	FULL	Memory buffer
CRYPTO_MEM_BUFF1666	0x40109A08	FULL	Memory buffer
CRYPTO_MEM_BUFF1667	0x40109A0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1668	0x40109A10	FULL	Memory buffer
CRYPTO_MEM_BUFF1669	0x40109A14	FULL	Memory buffer
CRYPTO_MEM_BUFF1670	0x40109A18	FULL	Memory buffer
CRYPTO_MEM_BUFF1671	0x40109A1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1672	0x40109A20	FULL	Memory buffer
CRYPTO_MEM_BUFF1673	0x40109A24	FULL	Memory buffer
CRYPTO_MEM_BUFF1674	0x40109A28	FULL	Memory buffer
CRYPTO_MEM_BUFF1675	0x40109A2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1676	0x40109A30	FULL	Memory buffer
CRYPTO_MEM_BUFF1677	0x40109A34	FULL	Memory buffer
CRYPTO_MEM_BUFF1678	0x40109A38	FULL	Memory buffer
CRYPTO_MEM_BUFF1679	0x40109A3C	FULL	Memory buffer
CRYPTO_MEM_BUFF1680	0x40109A40	FULL	Memory buffer
CRYPTO_MEM_BUFF1681	0x40109A44	FULL	Memory buffer
CRYPTO_MEM_BUFF1682	0x40109A48	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1683	0x40109A4C	FULL	Memory buffer
CRYPTO_MEM_BUFF1684	0x40109A50	FULL	Memory buffer
CRYPTO_MEM_BUFF1685	0x40109A54	FULL	Memory buffer
CRYPTO_MEM_BUFF1686	0x40109A58	FULL	Memory buffer
CRYPTO_MEM_BUFF1687	0x40109A5C	FULL	Memory buffer
CRYPTO_MEM_BUFF1688	0x40109A60	FULL	Memory buffer
CRYPTO_MEM_BUFF1689	0x40109A64	FULL	Memory buffer
CRYPTO_MEM_BUFF1690	0x40109A68	FULL	Memory buffer
CRYPTO_MEM_BUFF1691	0x40109A6C	FULL	Memory buffer
CRYPTO_MEM_BUFF1692	0x40109A70	FULL	Memory buffer
CRYPTO_MEM_BUFF1693	0x40109A74	FULL	Memory buffer
CRYPTO_MEM_BUFF1694	0x40109A78	FULL	Memory buffer
CRYPTO_MEM_BUFF1695	0x40109A7C	FULL	Memory buffer
CRYPTO_MEM_BUFF1696	0x40109A80	FULL	Memory buffer
CRYPTO_MEM_BUFF1697	0x40109A84	FULL	Memory buffer
CRYPTO_MEM_BUFF1698	0x40109A88	FULL	Memory buffer
CRYPTO_MEM_BUFF1699	0x40109A8C	FULL	Memory buffer
CRYPTO_MEM_BUFF1700	0x40109A90	FULL	Memory buffer
CRYPTO_MEM_BUFF1701	0x40109A94	FULL	Memory buffer
CRYPTO_MEM_BUFF1702	0x40109A98	FULL	Memory buffer
CRYPTO_MEM_BUFF1703	0x40109A9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1704	0x40109AA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1705	0x40109AA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1706	0x40109AA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1707	0x40109AAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1708	0x40109AB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1709	0x40109AB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1710	0x40109AB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1711	0x40109ABC	FULL	Memory buffer
CRYPTO_MEM_BUFF1712	0x40109AC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1713	0x40109AC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1714	0x40109AC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1715	0x40109ACC	FULL	Memory buffer
CRYPTO_MEM_BUFF1716	0x40109AD0	FULL	Memory buffer
CRYPTO_MEM_BUFF1717	0x40109AD4	FULL	Memory buffer
CRYPTO_MEM_BUFF1718	0x40109AD8	FULL	Memory buffer
CRYPTO_MEM_BUFF1719	0x40109ADC	FULL	Memory buffer
CRYPTO_MEM_BUFF1720	0x40109AE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1721	0x40109AE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1722	0x40109AE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1723	0x40109AEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1724	0x40109AF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1725	0x40109AF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1726	0x40109AF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1727	0x40109AFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1728	0x40109B00	FULL	Memory buffer
CRYPTO_MEM_BUFF1729	0x40109B04	FULL	Memory buffer
CRYPTO_MEM_BUFF1730	0x40109B08	FULL	Memory buffer
CRYPTO_MEM_BUFF1731	0x40109B0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1732	0x40109B10	FULL	Memory buffer
CRYPTO_MEM_BUFF1733	0x40109B14	FULL	Memory buffer
CRYPTO_MEM_BUFF1734	0x40109B18	FULL	Memory buffer
CRYPTO_MEM_BUFF1735	0x40109B1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1736	0x40109B20	FULL	Memory buffer
CRYPTO_MEM_BUFF1737	0x40109B24	FULL	Memory buffer
CRYPTO_MEM_BUFF1738	0x40109B28	FULL	Memory buffer
CRYPTO_MEM_BUFF1739	0x40109B2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1740	0x40109B30	FULL	Memory buffer
CRYPTO_MEM_BUFF1741	0x40109B34	FULL	Memory buffer
CRYPTO_MEM_BUFF1742	0x40109B38	FULL	Memory buffer
CRYPTO_MEM_BUFF1743	0x40109B3C	FULL	Memory buffer
CRYPTO_MEM_BUFF1744	0x40109B40	FULL	Memory buffer
CRYPTO_MEM_BUFF1745	0x40109B44	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1746	0x40109B48	FULL	Memory buffer
CRYPTO_MEM_BUFF1747	0x40109B4C	FULL	Memory buffer
CRYPTO_MEM_BUFF1748	0x40109B50	FULL	Memory buffer
CRYPTO_MEM_BUFF1749	0x40109B54	FULL	Memory buffer
CRYPTO_MEM_BUFF1750	0x40109B58	FULL	Memory buffer
CRYPTO_MEM_BUFF1751	0x40109B5C	FULL	Memory buffer
CRYPTO_MEM_BUFF1752	0x40109B60	FULL	Memory buffer
CRYPTO_MEM_BUFF1753	0x40109B64	FULL	Memory buffer
CRYPTO_MEM_BUFF1754	0x40109B68	FULL	Memory buffer
CRYPTO_MEM_BUFF1755	0x40109B6C	FULL	Memory buffer
CRYPTO_MEM_BUFF1756	0x40109B70	FULL	Memory buffer
CRYPTO_MEM_BUFF1757	0x40109B74	FULL	Memory buffer
CRYPTO_MEM_BUFF1758	0x40109B78	FULL	Memory buffer
CRYPTO_MEM_BUFF1759	0x40109B7C	FULL	Memory buffer
CRYPTO_MEM_BUFF1760	0x40109B80	FULL	Memory buffer
CRYPTO_MEM_BUFF1761	0x40109B84	FULL	Memory buffer
CRYPTO_MEM_BUFF1762	0x40109B88	FULL	Memory buffer
CRYPTO_MEM_BUFF1763	0x40109B8C	FULL	Memory buffer
CRYPTO_MEM_BUFF1764	0x40109B90	FULL	Memory buffer
CRYPTO_MEM_BUFF1765	0x40109B94	FULL	Memory buffer
CRYPTO_MEM_BUFF1766	0x40109B98	FULL	Memory buffer
CRYPTO_MEM_BUFF1767	0x40109B9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1768	0x40109BA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1769	0x40109BA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1770	0x40109BA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1771	0x40109BAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1772	0x40109BB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1773	0x40109BB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1774	0x40109BB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1775	0x40109BBC	FULL	Memory buffer
CRYPTO_MEM_BUFF1776	0x40109BC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1777	0x40109BC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1778	0x40109BC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1779	0x40109BCC	FULL	Memory buffer
CRYPTO_MEM_BUFF1780	0x40109BD0	FULL	Memory buffer
CRYPTO_MEM_BUFF1781	0x40109BD4	FULL	Memory buffer
CRYPTO_MEM_BUFF1782	0x40109BD8	FULL	Memory buffer
CRYPTO_MEM_BUFF1783	0x40109BDC	FULL	Memory buffer
CRYPTO_MEM_BUFF1784	0x40109BE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1785	0x40109BE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1786	0x40109BE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1787	0x40109BEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1788	0x40109BF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1789	0x40109BF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1790	0x40109BF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1791	0x40109BFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1792	0x40109C00	FULL	Memory buffer
CRYPTO_MEM_BUFF1793	0x40109C04	FULL	Memory buffer
CRYPTO_MEM_BUFF1794	0x40109C08	FULL	Memory buffer
CRYPTO_MEM_BUFF1795	0x40109C0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1796	0x40109C10	FULL	Memory buffer
CRYPTO_MEM_BUFF1797	0x40109C14	FULL	Memory buffer
CRYPTO_MEM_BUFF1798	0x40109C18	FULL	Memory buffer
CRYPTO_MEM_BUFF1799	0x40109C1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1800	0x40109C20	FULL	Memory buffer
CRYPTO_MEM_BUFF1801	0x40109C24	FULL	Memory buffer
CRYPTO_MEM_BUFF1802	0x40109C28	FULL	Memory buffer
CRYPTO_MEM_BUFF1803	0x40109C2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1804	0x40109C30	FULL	Memory buffer
CRYPTO_MEM_BUFF1805	0x40109C34	FULL	Memory buffer
CRYPTO_MEM_BUFF1806	0x40109C38	FULL	Memory buffer
CRYPTO_MEM_BUFF1807	0x40109C3C	FULL	Memory buffer
CRYPTO_MEM_BUFF1808	0x40109C40	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1809	0x40109C44	FULL	Memory buffer
CRYPTO_MEM_BUFF1810	0x40109C48	FULL	Memory buffer
CRYPTO_MEM_BUFF1811	0x40109C4C	FULL	Memory buffer
CRYPTO_MEM_BUFF1812	0x40109C50	FULL	Memory buffer
CRYPTO_MEM_BUFF1813	0x40109C54	FULL	Memory buffer
CRYPTO_MEM_BUFF1814	0x40109C58	FULL	Memory buffer
CRYPTO_MEM_BUFF1815	0x40109C5C	FULL	Memory buffer
CRYPTO_MEM_BUFF1816	0x40109C60	FULL	Memory buffer
CRYPTO_MEM_BUFF1817	0x40109C64	FULL	Memory buffer
CRYPTO_MEM_BUFF1818	0x40109C68	FULL	Memory buffer
CRYPTO_MEM_BUFF1819	0x40109C6C	FULL	Memory buffer
CRYPTO_MEM_BUFF1820	0x40109C70	FULL	Memory buffer
CRYPTO_MEM_BUFF1821	0x40109C74	FULL	Memory buffer
CRYPTO_MEM_BUFF1822	0x40109C78	FULL	Memory buffer
CRYPTO_MEM_BUFF1823	0x40109C7C	FULL	Memory buffer
CRYPTO_MEM_BUFF1824	0x40109C80	FULL	Memory buffer
CRYPTO_MEM_BUFF1825	0x40109C84	FULL	Memory buffer
CRYPTO_MEM_BUFF1826	0x40109C88	FULL	Memory buffer
CRYPTO_MEM_BUFF1827	0x40109C8C	FULL	Memory buffer
CRYPTO_MEM_BUFF1828	0x40109C90	FULL	Memory buffer
CRYPTO_MEM_BUFF1829	0x40109C94	FULL	Memory buffer
CRYPTO_MEM_BUFF1830	0x40109C98	FULL	Memory buffer
CRYPTO_MEM_BUFF1831	0x40109C9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1832	0x40109CA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1833	0x40109CA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1834	0x40109CA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1835	0x40109CAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1836	0x40109CB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1837	0x40109CB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1838	0x40109CB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1839	0x40109CBC	FULL	Memory buffer
CRYPTO_MEM_BUFF1840	0x40109CC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1841	0x40109CC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1842	0x40109CC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1843	0x40109CC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1844	0x40109CD0	FULL	Memory buffer
CRYPTO_MEM_BUFF1845	0x40109CD4	FULL	Memory buffer
CRYPTO_MEM_BUFF1846	0x40109CD8	FULL	Memory buffer
CRYPTO_MEM_BUFF1847	0x40109CDC	FULL	Memory buffer
CRYPTO_MEM_BUFF1848	0x40109CE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1849	0x40109CE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1850	0x40109CE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1851	0x40109CEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1852	0x40109CF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1853	0x40109CF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1854	0x40109CF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1855	0x40109CFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1856	0x40109D00	FULL	Memory buffer
CRYPTO_MEM_BUFF1857	0x40109D04	FULL	Memory buffer
CRYPTO_MEM_BUFF1858	0x40109D08	FULL	Memory buffer
CRYPTO_MEM_BUFF1859	0x40109D0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1860	0x40109D10	FULL	Memory buffer
CRYPTO_MEM_BUFF1861	0x40109D14	FULL	Memory buffer
CRYPTO_MEM_BUFF1862	0x40109D18	FULL	Memory buffer
CRYPTO_MEM_BUFF1863	0x40109D1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1864	0x40109D20	FULL	Memory buffer
CRYPTO_MEM_BUFF1865	0x40109D24	FULL	Memory buffer
CRYPTO_MEM_BUFF1866	0x40109D28	FULL	Memory buffer
CRYPTO_MEM_BUFF1867	0x40109D2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1868	0x40109D30	FULL	Memory buffer
CRYPTO_MEM_BUFF1869	0x40109D34	FULL	Memory buffer
CRYPTO_MEM_BUFF1870	0x40109D38	FULL	Memory buffer
CRYPTO_MEM_BUFF1871	0x40109D3C	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1872	0x40109D40	FULL	Memory buffer
CRYPTO_MEM_BUFF1873	0x40109D44	FULL	Memory buffer
CRYPTO_MEM_BUFF1874	0x40109D48	FULL	Memory buffer
CRYPTO_MEM_BUFF1875	0x40109D4C	FULL	Memory buffer
CRYPTO_MEM_BUFF1876	0x40109D50	FULL	Memory buffer
CRYPTO_MEM_BUFF1877	0x40109D54	FULL	Memory buffer
CRYPTO_MEM_BUFF1878	0x40109D58	FULL	Memory buffer
CRYPTO_MEM_BUFF1879	0x40109D5C	FULL	Memory buffer
CRYPTO_MEM_BUFF1880	0x40109D60	FULL	Memory buffer
CRYPTO_MEM_BUFF1881	0x40109D64	FULL	Memory buffer
CRYPTO_MEM_BUFF1882	0x40109D68	FULL	Memory buffer
CRYPTO_MEM_BUFF1883	0x40109D6C	FULL	Memory buffer
CRYPTO_MEM_BUFF1884	0x40109D70	FULL	Memory buffer
CRYPTO_MEM_BUFF1885	0x40109D74	FULL	Memory buffer
CRYPTO_MEM_BUFF1886	0x40109D78	FULL	Memory buffer
CRYPTO_MEM_BUFF1887	0x40109D7C	FULL	Memory buffer
CRYPTO_MEM_BUFF1888	0x40109D80	FULL	Memory buffer
CRYPTO_MEM_BUFF1889	0x40109D84	FULL	Memory buffer
CRYPTO_MEM_BUFF1890	0x40109D88	FULL	Memory buffer
CRYPTO_MEM_BUFF1891	0x40109D8C	FULL	Memory buffer
CRYPTO_MEM_BUFF1892	0x40109D90	FULL	Memory buffer
CRYPTO_MEM_BUFF1893	0x40109D94	FULL	Memory buffer
CRYPTO_MEM_BUFF1894	0x40109D98	FULL	Memory buffer
CRYPTO_MEM_BUFF1895	0x40109D9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1896	0x40109DA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1897	0x40109DA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1898	0x40109DA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1899	0x40109DAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1900	0x40109DB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1901	0x40109DB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1902	0x40109DB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1903	0x40109DBC	FULL	Memory buffer
CRYPTO_MEM_BUFF1904	0x40109DC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1905	0x40109DC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1906	0x40109DC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1907	0x40109DCC	FULL	Memory buffer
CRYPTO_MEM_BUFF1908	0x40109DD0	FULL	Memory buffer
CRYPTO_MEM_BUFF1909	0x40109DD4	FULL	Memory buffer
CRYPTO_MEM_BUFF1910	0x40109DD8	FULL	Memory buffer
CRYPTO_MEM_BUFF1911	0x40109DDC	FULL	Memory buffer
CRYPTO_MEM_BUFF1912	0x40109DE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1913	0x40109DE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1914	0x40109DE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1915	0x40109DEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1916	0x40109DF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1917	0x40109DF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1918	0x40109DF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1919	0x40109DFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1920	0x40109E00	FULL	Memory buffer
CRYPTO_MEM_BUFF1921	0x40109E04	FULL	Memory buffer
CRYPTO_MEM_BUFF1922	0x40109E08	FULL	Memory buffer
CRYPTO_MEM_BUFF1923	0x40109E0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1924	0x40109E10	FULL	Memory buffer
CRYPTO_MEM_BUFF1925	0x40109E14	FULL	Memory buffer
CRYPTO_MEM_BUFF1926	0x40109E18	FULL	Memory buffer
CRYPTO_MEM_BUFF1927	0x40109E1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1928	0x40109E20	FULL	Memory buffer
CRYPTO_MEM_BUFF1929	0x40109E24	FULL	Memory buffer
CRYPTO_MEM_BUFF1930	0x40109E28	FULL	Memory buffer
CRYPTO_MEM_BUFF1931	0x40109E2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1932	0x40109E30	FULL	Memory buffer
CRYPTO_MEM_BUFF1933	0x40109E34	FULL	Memory buffer
CRYPTO_MEM_BUFF1934	0x40109E38	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1935	0x40109E3C	FULL	Memory buffer
CRYPTO_MEM_BUFF1936	0x40109E40	FULL	Memory buffer
CRYPTO_MEM_BUFF1937	0x40109E44	FULL	Memory buffer
CRYPTO_MEM_BUFF1938	0x40109E48	FULL	Memory buffer
CRYPTO_MEM_BUFF1939	0x40109E4C	FULL	Memory buffer
CRYPTO_MEM_BUFF1940	0x40109E50	FULL	Memory buffer
CRYPTO_MEM_BUFF1941	0x40109E54	FULL	Memory buffer
CRYPTO_MEM_BUFF1942	0x40109E58	FULL	Memory buffer
CRYPTO_MEM_BUFF1943	0x40109E5C	FULL	Memory buffer
CRYPTO_MEM_BUFF1944	0x40109E60	FULL	Memory buffer
CRYPTO_MEM_BUFF1945	0x40109E64	FULL	Memory buffer
CRYPTO_MEM_BUFF1946	0x40109E68	FULL	Memory buffer
CRYPTO_MEM_BUFF1947	0x40109E6C	FULL	Memory buffer
CRYPTO_MEM_BUFF1948	0x40109E70	FULL	Memory buffer
CRYPTO_MEM_BUFF1949	0x40109E74	FULL	Memory buffer
CRYPTO_MEM_BUFF1950	0x40109E78	FULL	Memory buffer
CRYPTO_MEM_BUFF1951	0x40109E7C	FULL	Memory buffer
CRYPTO_MEM_BUFF1952	0x40109E80	FULL	Memory buffer
CRYPTO_MEM_BUFF1953	0x40109E84	FULL	Memory buffer
CRYPTO_MEM_BUFF1954	0x40109E88	FULL	Memory buffer
CRYPTO_MEM_BUFF1955	0x40109E8C	FULL	Memory buffer
CRYPTO_MEM_BUFF1956	0x40109E90	FULL	Memory buffer
CRYPTO_MEM_BUFF1957	0x40109E94	FULL	Memory buffer
CRYPTO_MEM_BUFF1958	0x40109E98	FULL	Memory buffer
CRYPTO_MEM_BUFF1959	0x40109E9C	FULL	Memory buffer
CRYPTO_MEM_BUFF1960	0x40109EA0	FULL	Memory buffer
CRYPTO_MEM_BUFF1961	0x40109EA4	FULL	Memory buffer
CRYPTO_MEM_BUFF1962	0x40109EA8	FULL	Memory buffer
CRYPTO_MEM_BUFF1963	0x40109EAC	FULL	Memory buffer
CRYPTO_MEM_BUFF1964	0x40109EB0	FULL	Memory buffer
CRYPTO_MEM_BUFF1965	0x40109EB4	FULL	Memory buffer
CRYPTO_MEM_BUFF1966	0x40109EB8	FULL	Memory buffer
CRYPTO_MEM_BUFF1967	0x40109EBC	FULL	Memory buffer
CRYPTO_MEM_BUFF1968	0x40109EC0	FULL	Memory buffer
CRYPTO_MEM_BUFF1969	0x40109EC4	FULL	Memory buffer
CRYPTO_MEM_BUFF1970	0x40109EC8	FULL	Memory buffer
CRYPTO_MEM_BUFF1971	0x40109ECC	FULL	Memory buffer
CRYPTO_MEM_BUFF1972	0x40109ED0	FULL	Memory buffer
CRYPTO_MEM_BUFF1973	0x40109ED4	FULL	Memory buffer
CRYPTO_MEM_BUFF1974	0x40109ED8	FULL	Memory buffer
CRYPTO_MEM_BUFF1975	0x40109EDC	FULL	Memory buffer
CRYPTO_MEM_BUFF1976	0x40109EE0	FULL	Memory buffer
CRYPTO_MEM_BUFF1977	0x40109EE4	FULL	Memory buffer
CRYPTO_MEM_BUFF1978	0x40109EE8	FULL	Memory buffer
CRYPTO_MEM_BUFF1979	0x40109EEC	FULL	Memory buffer
CRYPTO_MEM_BUFF1980	0x40109EF0	FULL	Memory buffer
CRYPTO_MEM_BUFF1981	0x40109EF4	FULL	Memory buffer
CRYPTO_MEM_BUFF1982	0x40109EF8	FULL	Memory buffer
CRYPTO_MEM_BUFF1983	0x40109EFC	FULL	Memory buffer
CRYPTO_MEM_BUFF1984	0x40109F00	FULL	Memory buffer
CRYPTO_MEM_BUFF1985	0x40109F04	FULL	Memory buffer
CRYPTO_MEM_BUFF1986	0x40109F08	FULL	Memory buffer
CRYPTO_MEM_BUFF1987	0x40109F0C	FULL	Memory buffer
CRYPTO_MEM_BUFF1988	0x40109F10	FULL	Memory buffer
CRYPTO_MEM_BUFF1989	0x40109F14	FULL	Memory buffer
CRYPTO_MEM_BUFF1990	0x40109F18	FULL	Memory buffer
CRYPTO_MEM_BUFF1991	0x40109F1C	FULL	Memory buffer
CRYPTO_MEM_BUFF1992	0x40109F20	FULL	Memory buffer
CRYPTO_MEM_BUFF1993	0x40109F24	FULL	Memory buffer
CRYPTO_MEM_BUFF1994	0x40109F28	FULL	Memory buffer
CRYPTO_MEM_BUFF1995	0x40109F2C	FULL	Memory buffer
CRYPTO_MEM_BUFF1996	0x40109F30	FULL	Memory buffer
CRYPTO_MEM_BUFF1997	0x40109F34	FULL	Memory buffer

Register Name	Address	Permission	Description
CRYPTO_MEM_BUFF1998	0x40109F38	FULL	Memory buffer
CRYPTO_MEM_BUFF1999	0x40109F3C	FULL	Memory buffer
CRYPTO_MEM_BUFF2000	0x40109F40	FULL	Memory buffer
CRYPTO_MEM_BUFF2001	0x40109F44	FULL	Memory buffer
CRYPTO_MEM_BUFF2002	0x40109F48	FULL	Memory buffer
CRYPTO_MEM_BUFF2003	0x40109F4C	FULL	Memory buffer
CRYPTO_MEM_BUFF2004	0x40109F50	FULL	Memory buffer
CRYPTO_MEM_BUFF2005	0x40109F54	FULL	Memory buffer
CRYPTO_MEM_BUFF2006	0x40109F58	FULL	Memory buffer
CRYPTO_MEM_BUFF2007	0x40109F5C	FULL	Memory buffer
CRYPTO_MEM_BUFF2008	0x40109F60	FULL	Memory buffer
CRYPTO_MEM_BUFF2009	0x40109F64	FULL	Memory buffer
CRYPTO_MEM_BUFF2010	0x40109F68	FULL	Memory buffer
CRYPTO_MEM_BUFF2011	0x40109F6C	FULL	Memory buffer
CRYPTO_MEM_BUFF2012	0x40109F70	FULL	Memory buffer
CRYPTO_MEM_BUFF2013	0x40109F74	FULL	Memory buffer
CRYPTO_MEM_BUFF2014	0x40109F78	FULL	Memory buffer
CRYPTO_MEM_BUFF2015	0x40109F7C	FULL	Memory buffer
CRYPTO_MEM_BUFF2016	0x40109F80	FULL	Memory buffer
CRYPTO_MEM_BUFF2017	0x40109F84	FULL	Memory buffer
CRYPTO_MEM_BUFF2018	0x40109F88	FULL	Memory buffer
CRYPTO_MEM_BUFF2019	0x40109F8C	FULL	Memory buffer
CRYPTO_MEM_BUFF2020	0x40109F90	FULL	Memory buffer
CRYPTO_MEM_BUFF2021	0x40109F94	FULL	Memory buffer
CRYPTO_MEM_BUFF2022	0x40109F98	FULL	Memory buffer
CRYPTO_MEM_BUFF2023	0x40109F9C	FULL	Memory buffer
CRYPTO_MEM_BUFF2024	0x40109FA0	FULL	Memory buffer
CRYPTO_MEM_BUFF2025	0x40109FA4	FULL	Memory buffer
CRYPTO_MEM_BUFF2026	0x40109FA8	FULL	Memory buffer
CRYPTO_MEM_BUFF2027	0x40109FAC	FULL	Memory buffer
CRYPTO_MEM_BUFF2028	0x40109FB0	FULL	Memory buffer
CRYPTO_MEM_BUFF2029	0x40109FB4	FULL	Memory buffer
CRYPTO_MEM_BUFF2030	0x40109FB8	FULL	Memory buffer
CRYPTO_MEM_BUFF2031	0x40109FBC	FULL	Memory buffer
CRYPTO_MEM_BUFF2032	0x40109FC0	FULL	Memory buffer
CRYPTO_MEM_BUFF2033	0x40109FC4	FULL	Memory buffer
CRYPTO_MEM_BUFF2034	0x40109FC8	FULL	Memory buffer
CRYPTO_MEM_BUFF2035	0x40109FCC	FULL	Memory buffer
CRYPTO_MEM_BUFF2036	0x40109FD0	FULL	Memory buffer
CRYPTO_MEM_BUFF2037	0x40109FD4	FULL	Memory buffer
CRYPTO_MEM_BUFF2038	0x40109FD8	FULL	Memory buffer
CRYPTO_MEM_BUFF2039	0x40109FDC	FULL	Memory buffer
CRYPTO_MEM_BUFF2040	0x40109FE0	FULL	Memory buffer
CRYPTO_MEM_BUFF2041	0x40109FE4	FULL	Memory buffer
CRYPTO_MEM_BUFF2042	0x40109FE8	FULL	Memory buffer
CRYPTO_MEM_BUFF2043	0x40109FEC	FULL	Memory buffer
CRYPTO_MEM_BUFF2044	0x40109FF0	FULL	Memory buffer
CRYPTO_MEM_BUFF2045	0x40109FF4	FULL	Memory buffer
CRYPTO_MEM_BUFF2046	0x40109FF8	FULL	Memory buffer
CRYPTO_MEM_BUFF2047	0x40109FFC	FULL	Memory buffer

6.1 Register Details

6.1.1 CRYPTO_CTL

Description: Control
Address: 0x40100000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10002

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:2]		NS [1:1]	P [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						ECC_INJ_EN [17:17]	ECC_EN [16:16]
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	0	User/privileged access control: '0': user mode. '1': privileged mode. This field is set with the user/privileged access control of the transaction that writes this register; i.e. the access control is inherited from the write transaction and not specified by the transaction write data. All IP master transactions use the P field for the user/privileged access control ('hprot[1]').
1	NS	RW	RW	1	Secure/on-secure access control: '0': secure. '1': non-secure. This field is set with the secure/non-secure access control of the transaction that writes this register; i.e. the access control is inherited from the write transaction and not specified by the transaction write data. All IP master transactions use the NS field for the secure/non-secure access control ('hprot[4]').

Bits	Name	SW	HW	Default or Enum	Description
4:7	PC	RW	RW	0	Protection context. This field is set with the protection context of the transaction that writes this register; i.e. the context is inherited from the write transaction and not specified by the transaction write data. All IP master transactions use the PC field for the protection context. There is one exception: the LOAD_DEV_KEY instruction IP master transactions are always performed with protection context '0'.
16	ECC_EN	RW	RW	1	Enable ECC checking: '0': Disabled. '1': Enabled.
17	ECC_INJ_EN	RW	RW	0	Enable parity injection for SRAM. When '1', the parity (ECC_CTL.PARITY) is used when a full 32-bit write is done to the ECC_CTL.WORD_ADDR word address of the SRAM.
31	ENABLED	RW	RW	0	IP enable: '0': Disabled. All non-retention registers (command and status registers, instruct FIFO, internal component state machines) are reset to their default value when the IP is disabled. All retention registers retain their value when the IP is disabled. '1': Enabled. When the IP is enabled, the IP register buffer is set to '0'.
	DISABLED			0	N/A
	ENABLED			1	N/A

6.1.2 CRYPTO_RAM_PWR_CTL

Description: SRAM power control
Address: 0x40100008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	3	Set power mode for memory buffer SRAM.
	OFF			0	See CM4_PWR_CTL
	RESERVED			1	undefined
	RETAINED			2	See CM4_PWR_CTL
	ENABLED			3	See CM4_PWR_CTL

6.1.3 CRYPTO_RAM_PWR_DELAY_CTL

Description: SRAM power delay control
Address: 0x4010000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x96

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						UP [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	UP	RW	RW	150	Number clock cycles delay needed after power domain power up

6.1.4 CRYPTO_ECC_CTL

Description: ECC control
Address: 0x40100010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORD_ADDR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			WORD_ADDR [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	PARITY [31:25]							None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:12	WORD_ADDR	RW	RW	0	Specifies the word address where the parity is injected. - On a 32-bit write access to this SRAM address and when CTL.ECC_INJ_EN bit is '1', the parity (PARITY) is injected.
25:31	PARITY	RW	RW	0	ECC parity to use for ECC error injection at address WORD_ADDR.

6.1.5 CRYPTO_ERROR_STATUS0

Description: Error status 0
Address: 0x40100020
Offset: 0x20
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	R	R	Undefined	Specifies error description information. - For INSTR_OPC_ERROR/ INSTR_CC_ERROR/ INSTR_DEV_KEY_ERROR: - Violating instruction (from instruction FIFO). - For BUS_ERROR: - Violating transfer, address.

6.1.6 CRYPTO_ERROR_STATUS1

Description: Error status 1
Address: 0x40100024
Offset: 0x24
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA24 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA24 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA24 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:27]				IDX [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	DATA24	R	R	Undefined	Specifies error description information. - For BUS_ERROR: - Violating transfer, read attribute (DATA[0]). - Violating transfer, size attribute (DATA[5:4]). '0': 8-bit transfer, '1': 16 bits transfer, '2': 32-bit transfer.
24:26	IDX	R	R	Undefined	Error source: '0': INSTR_OPC_ERROR (instruction FIFO decoder error). '1': INSTR_CC_ERROR (instruction FIFO decoder, VU CC error). '2': BUS_ERROR (bus master interface AHB-Lite bus error). '3': TR_AP_DETECT_ERROR. '4': TR_RC_DETECT_ERROR. '5': INSTR_DEV_KEY_ERROR. '6'-'7': Undefined.
31	VALID	RW	RW	0	Specifies if ERROR_STATUS0 and ERROR_STATUS1 specify valid error information. No new error information is captured as long as VALID is '1'; i.e. the error information of the first detected error is NOT overwritten.

6.1.7 CRYPTO_INTR

Description: Interrupt register
Address: 0x40100100
Offset: 0x100
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PR_DATA_A AVAILABLE [4:4]	TR_DATA_A AVAILABLE [3:3]	TR_INITIALIZED [2:2]	INSTR_FF_OVERFLOW [1:1]	INSTR_FF_LEVEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		INSTR_DEV_KEY_ERROR [21:21]	TR_RC_DETECT_ERROR [20:20]	TR_AP_DETECT_ERROR [19:19]	BUS_ERROR [18:18]	INSTR_CC_ERROR [17:17]	INSTR_OPC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INSTR_FF_LEVEL	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the instruction FIFO event is activated.
1	INSTR_FF_OVERFLOW	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the instruction FIFO overflows (an attempt is made to write to a full FIFO).
2	TR_INITIALIZED	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the true random number generator is initialized.
3	TR_DATA_AVAILABLE	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the true random number generator has generated a data value of the specified bit size.
4	PR_DATA_AVAILABLE	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the pseudo random number generator has generated a data value.
16	INSTR_OPC_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the instruction decoder encounters an instruction with a non-defined operation code (opcode). When the interrupt cause is activated, HW sets INSTR_FF_CTL.CLEAR to '1'.
17	INSTR_CC_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the instruction decoder encounters an instruction with a non-defined condition code. This error is only generated for VU instructions. When the interrupt cause is activated, HW sets INSTR_FF_CTL.CLEAR to '1'.

Bits	Name	SW	HW	Default or Enum	Description
18	BUS_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when a AHB-Lite bus error is observed on the AHB-Lite master interface. When the interrupt cause is activated, HW sets INSTR_FF_CTL.CLEAR to '1'.
19	TR_AP_DETECT_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the true random number generator monitor adaptive proportion test detects a repetition of a specific bit value.
20	TR_RC_DETECT_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the true random number generator monitor adaptive proportion test detects a disproportionate occurrence of a specific bit value.
21	INSTR_DEV_KEY_ERROR	RW1C	RW1C	0	This interrupt cause is activated (HW sets the field to '1') when the LOAD_DEV_KEY instruction tries to load a device key whose DEV_KEY_ADDR_CTL.VALID or DEV_KEY_CTL.ALLOWED is set to '0'.

6.1.8 CRYPTO_INTR_SET

Description: Interrupt set register

Address: 0x40100104

Offset: 0x104

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects the interrupt request register. For debug purposes, SW can write a '1' to activate a specific interrupt cause (this allows for debug of the SW ISR, without requiring a HW command/operation).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PR_DATA_A AVAILABLE [4:4]	TR_DATA_A AVAILABLE [3:3]	TR_INITIALIZED [2:2]	INSTR_FF_OVERFLOW [1:1]	INSTR_FF_LEVEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		INSTR_DEV_KEY_ERROR [21:21]	TR_RC_DETECT_ERROR [20:20]	TR_AP_DETECT_ERROR [19:19]	BUS_ERROR [18:18]	INSTR_CC_ERROR [17:17]	INSTR_OPC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INSTR_FF_LEVEL	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
1	INSTR_FF_OVERFLOW	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
2	TR_INITIALIZED	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
3	TR_DATA_AVAILABLE	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
4	PR_DATA_AVAILABLE	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
16	INSTR_OPC_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
17	INSTR_CC_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
18	BUS_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
19	TR_AP_DETECT_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
20	TR_RC_DETECT_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.
21	INSTR_DEV_KEY_ERROR	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in interrupt request register.

6.1.9 CRYPTO_INTR_MASK

Description: Interrupt mask register
Address: 0x40100108
Offset: 0x108
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PR_DATA_A AVAILABLE [4:4]	TR_DATA_A AVAILABLE [3:3]	TR_INITIALIZED [2:2]	INSTR_FF_OVERFLOW [1:1]	INSTR_FF_LEVEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		INSTR_DEV_KEY_ERROR [21:21]	TR_RC_DETECT_ERROR [20:20]	TR_AP_DETECT_ERROR [19:19]	BUS_ERROR [18:18]	INSTR_CC_ERROR [17:17]	INSTR_OPC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INSTR_FF_LEVEL	RW	RW	0	Mask bit for corresponding field in interrupt request register.
1	INSTR_FF_OVERFLOW	RW	RW	0	Mask bit for corresponding field in interrupt request register.
2	TR_INITIALIZED	RW	RW	0	Mask bit for corresponding field in interrupt request register.
3	TR_DATA_AVAILABLE	RW	RW	0	Mask bit for corresponding field in interrupt request register.
4	PR_DATA_AVAILABLE	RW	RW	0	Mask bit for corresponding field in interrupt request register.
16	INSTR_OPC_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.
17	INSTR_CC_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.
18	BUS_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.
19	TR_AP_DETECT_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.
20	TR_RC_DETECT_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.
21	INSTR_DEV_KEY_ERROR	RW	RW	0	Mask bit for corresponding field in interrupt request register.

6.1.10 CRYPTO_INTR_MASKED

Description: Interrupt masked register
Address: 0x4010010C
Offset: 0x10C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects 'a bitwise AND' between the interrupt request INTR and mask INTR_MASK registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PR_DATA_A AVAILABLE [4:4]	TR_DATA_A AVAILABLE [3:3]	TR_INITIALIZED [2:2]	INSTR_FF_OVERFLOW [1:1]	INSTR_FF_LEVEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		INSTR_DEV_KEY_ERROR [21:21]	TR_RC_DETECT_ERROR [20:20]	TR_AP_DETECT_ERROR [19:19]	BUS_ERROR [18:18]	INSTR_CC_ERROR [17:17]	INSTR_OPC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INSTR_FF_LEVEL	R	R	0	Logical and of corresponding request and mask bits.
1	INSTR_FF_OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
2	TR_INITIALIZED	R	R	0	Logical and of corresponding request and mask bits.
3	TR_DATA_AVAILABLE	R	R	0	Logical and of corresponding request and mask bits.
4	PR_DATA_AVAILABLE	R	R	0	Logical and of corresponding request and mask bits.
16	INSTR_OPC_ERROR	R	R	0	Logical and of corresponding request and mask bits.
17	INSTR_CC_ERROR	R	R	0	Logical and of corresponding request and mask bits.
18	BUS_ERROR	R	R	0	Logical and of corresponding request and mask bits.
19	TR_AP_DETECT_ERROR	R	R	0	Logical and of corresponding request and mask bits.
20	TR_RC_DETECT_ERROR	R	R	0	Logical and of corresponding request and mask bits.
21	INSTR_DEV_KEY_ERROR	R	R	0	Logical and of corresponding request and mask bits.

6.1.11 CRYPTO_PR_LFSR_CTL0

Description: Pseudo random LFSR control 0
Address: 0x40100200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD8959BC9

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LFSR32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LFSR32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LFSR32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	LFSR32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	LFSR32	RW	RW	363368340 1	State of a 32-bit Linear Feedback Shift Registers (LFSR) that is used to generate a pseudo random bit sequence. This register needs to be initialized by SW. The initialization value should be different from '0'. The three PR_LFSR_CTL registers represents the state of a 32-bit, 31-bit and 29-bit LFSR. Individually, these LFSRs generate a pseudo random bit sequence that repeats itself after $(2^{32})-1$, $(2^{31})-1$ and $(2^{29})-1$ bits. The numbers $(2^{32})-1$, $(2^{31})-1$ and $(2^{29})-1$ are relatively prime (their greatest common denominator is '1'). The three bit sequence are combined (XOR'd) into a single bitstream to create a pseudo random bit sequence that repeats itself after $((2^{32})-1) * ((2^{31})-1) * ((2^{29})-1)$ bits. The following polynomials are used: - 32-bit irreducible polynomial: $x^{32}+x^{30}+x^{26}+x^{25}+1$. - 31-bit irreducible polynomial: $x^{31}+x^{28}+1$. - 29-bit irreducible polynomial: $x^{29}+x^{27}+1$.

6.1.12 CRYPTO_PR_LFSR_CTL1

Description: Pseudo random LFSR control 1
Address: 0x40100204
Offset: 0x204
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2BB911F8

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LFSR31 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	LFSR31 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	LFSR31 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	LFSR31 [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:30	LFSR31	RW	RW	733549048	State of a 31-bit Linear Feedback Shift Registers (LFSR) that is used to generate a pseudo random bit sequence. See PR_LFSR_CTL0.

6.1.13 CRYPTO_PR_LFSR_CTL2

Description: Pseudo random LFSR control 2
Address: 0x40100208
Offset: 0x208
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x60C31B7

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LFSR29 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LFSR29 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LFSR29 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			LFSR29 [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:28	LFSR29	RW	RW	101462455	State of a 29-bit Linear Feedback Shift Registers (LFSR) that is used to generate a pseudo random bit sequence. See PR_LFSR_CTL0.

6.1.14 CRYPTO_PR_MAX_CTL

Description: Pseudo random maximum control
Address: 0x4010020C
Offset: 0x20C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	4294967295	Maximum value of to be generated random number

6.1.15 CRYPTO_PR_CMD

Description: Pseudo random command
Address: 0x40100210
Offset: 0x210
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	START	RW1S	RW1S	0	Pseudo random command. On a generated number, HW sets this field to '0' and sets INTR.PR_DATA_AVAILABLE to '1'.

6.1.16 CRYPTO_PR_RESULT

Description: Pseudo random result
Address: 0x40100218
Offset: 0x218
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	0	Result of a pseudo random number generation operation. The resulting value DATA is in the range [0, PR_MAX_CTL.DATA32]. The PR_DATA_AVAILABLE interrupt cause is activated when the number is generated. Note that SW can write this field. This functionality can be used prevent information leakage.

6.1.17 CRYPTO_TR_CTL0

Description: True random control 0
Address: 0x40100280
Offset: 0x280
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x30000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SAMPLE_CLOCK_DIV [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RED_CLOCK_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INIT_DELAY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		STOP_ON_RC_DETECT [29:29]	STOP_ON_AP_DETECT [28:28]	None [27:25]			VON_NEUMANN_CORR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SAMPLE_CLOCK_DIV	RW	RW	0	Specifies the clock divider that is used to sample oscillator data. This clock divider is wrt. 'clk_sys'. '0': sample clock is 'clk_sys'. '1': sample clock is 'clk_sys'/2. ... '255': sample clock is 'clk_sys'/256.
8:15	RED_CLOCK_DIV	RW	RW	0	Specifies the clock divider that is used to produce reduced bits. '0': 1 reduced bit is produced for each sample. '1': 1 reduced bit is produced for each 2 samples. ... '255': 1 reduced bit is produced for each 256 samples. The reduced bits are considered random bits and shifted into TR_RESULT0.DATA32.
16:23	INIT_DELAY	RW	RW	3	Specifies an initialization delay: number of removed/dropped samples before reduced bits are generated. This field should be programmed in the range [1, 255]. After starting the oscillators, at least the first 2 samples should be removed/dropped to clear the state of internal synchronizers. In addition, it is advised to drop at least the second 2 samples from the oscillators (to circumvent the semi-predictable oscillator startup behavior). This result in the default field value of '3'. Field encoding is as follows: '0': 1 sample is dropped. '1': 2 samples are dropped. ... '255': 256 samples are dropped. The TR_INITIALIZED interrupt cause is set to '1', when the initialization delay is passed.

Bits	Name	SW	HW	Default or Enum	Description
24	VON_NEUMANN_CORR	RW	RW	0	Specifies if the 'von Neumann corrector' is disabled or enabled: '0': disabled. '1': enabled. The 'von Neumann corrector' post-processes the reduced bits to remove a '0' or '1' bias. The corrector operates on reduced bit pairs ('oldest bit, newest bit'): '00': no bit is produced. '01': '0' bit is produced (oldest bit). '10': '1' bit is produced (oldest bit). '11': no bit is produced. Note that the corrector produces bits at a random pace and at a frequency that is 1/4 of the reduced bit frequency (reduced bits are processed in pairs, and half of the pairs do NOT produce a bit).
28	STOP_ON_AP_DETECT	RW	RW	0	Specifies if TRNG functionality is stopped on an adaptive proportion test detection (when HW sets INTR.TR_AP_DETECT to '1'): '0': Functionality is NOT stopped. '1': Functionality is stopped (TR_CTL1 fields are set to '0' by HW).
29	STOP_ON_RC_DETECT	RW	RW	0	Specifies if TRNG functionality is stopped on a repetition count test detection (when HW sets INTR.TR_RC_DETECT to '1'): '0': Functionality is NOT stopped. '1': Functionality is stopped (TR_CTL1 fields are set to '0' by HW).

6.1.18 CRYPTO_TR_CTL1

Description: True random control 1

Address: 0x40100284

Offset: 0x284

Retention: Retained

IsDeepSleep: No

Comment: A 'not enabled' ring oscillator is 'broken up' to prevent oscillation and reduce dynamic power consumption. Enabling more oscillators produces better random numbers, but increases power consumption. At least one oscillator needs to be enabled to produce random numbers.

HW clears these register fields on the following circumstances:

- TR_CTL0.STOP_ON_AP_DETECT is '1' and there is on an adaptive proportion test detection.

- TR_CTL0.STOP_ON_RC_DETECT is '1' and there is on an repetition count test detection.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		FIRO31_EN [5:5]	FIRO15_EN [4:4]	GARO31_EN [3:3]	GARO15_EN [2:2]	RO15_EN [1:1]	RO11_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RO11_EN	RW	RW	0	FW sets this field to '1' to enable the ring oscillator with 11 inverters.
1	RO15_EN	RW	RW	0	FW sets this field to '1' to enable the ring oscillator with 15 inverters.
2	GARO15_EN	RW	RW	0	FW sets this field to '1' to enable the fixed Galois ring oscillator with 15 inverters.
3	GARO31_EN	RW	RW	0	FW sets this field to '1' to enable the programmable Galois ring oscillator with up to 31 inverters. The TR_GARO_CTL register specifies the programmable polynomial.
4	FIRO15_EN	RW	RW	0	FW sets this field to '1' to enable the fixed Fibonacci ring oscillator with 15 inverters.
5	FIRO31_EN	RW	RW	0	FW sets this field to '1' to enable the programmable Fibonacci ring oscillator with up to 31 inverters. The TR_FIRO_CTL register specifies the programmable polynomial.

6.1.19 CRYPTO_TR_CTL2

Description: True random control 2
Address: 0x40100288
Offset: 0x288
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		SIZE [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	SIZE	RW	RW	0	Bit size of generated random number in TR_RESULT. Legal range is in [0, 32].

6.1.20 CRYPTO_TR_STATUS

Description: True random status
Address: 0x4010028C
Offset: 0x28C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INITIALIZ ED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INITIALIZED	R	R	0	Reflects the state of the true random number generator: '0': Not initialized (TR_CTL0.INIT_DELAY has NOT passed). '1': Initialized (TR_CTL0.INIT_DELAY has passed).

6.1.21 CRYPTO_TR_CMD

Description: True random command
Address: 0x40100290
Offset: 0x290
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	START	RW1S	RW1S	0	True random command. On completion of the command, HW sets this field to '0' and sets INTR.TR_DATA_AVAILABLE to '1' when: - A random number is generated in TR_RESULT. - All ring oscillators are off (per TR_CTL1). - A repetition count (RC) or adaptive proportion (AP) error is detected during the random number generation (INTR.TR_RC/AP_DETECT_ERROR). Note: On completion of the command, SW should check TR_CTL1 and INTR.TR_RC/AP_DETECT_ERROR to ensure that no unexpected error occurred during random number generation.

6.1.22 CRYPTO_TR_RESULT

Description: True random result
Address: 0x40100298
Offset: 0x298
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	0	Generated true random number. HW generates the number in the least significant bit positions (TR_CTL2.SIZE) of this field. The TR_DATA_AVAILABLE interrupt cause is activated when the number is generated. Note that SW can write this field. This functionality can be used prevent information leakage.

6.1.23 CRYPTO_TR_GARO_CTL

Description: True random GARO control
Address: 0x401002A0
Offset: 0x2A0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	POLYNOMIAL31 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	POLYNOMIAL31 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	POLYNOMIAL31 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	POLYNOMIAL31 [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:30	POLYNOMIAL31	RW	RW	0	Polynomial for programmable Galois ring oscillator. The polynomial is represented WITHOUT the high order bit (this bit is always assumed '1'). The polynomial should be aligned such that the more significant bits (bit 30 and down) contain the polynomial and the less significant bits (bit 0 and up) contain padding '0's.

6.1.24 CRYPTO_TR_FIRO_CTL

Description: True random FIRO control
Address: 0x401002A4
Offset: 0x2A4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	POLYNOMIAL31 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	POLYNOMIAL31 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	POLYNOMIAL31 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	POLYNOMIAL31 [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:30	POLYNOMIAL31	RW	RW	0	Polynomial for programmable Fibonacci ring oscillator. The polynomial is represented WITHOUT the high order bit (this bit is always assumed '1'). The polynomial should be aligned such that the more significant bits (bit 30 and down) contain the polynomial and the less significant bits (bit 0 and up) contain padding '0's.

6.1.25 CRYPTO_TR_MON_CTL

Description: True random monitor control
Address: 0x401002C0
Offset: 0x2C0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						BITSTREAM_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	BITSTREAM_SEL	RW	RW	2	Selection of the bitstream: '0': DAS bitstream. '1': RED bitstream. '2': TR bitstream. '3': Undefined.

6.1.26 CRYPTO_TR_MON_CMD

Description: True random monitor command
Address: 0x401002C8
Offset: 0x2C8
Retention: Not Retained
IsDeepSleep: No
Comment: SW should start the IP and RX tests after the initialization delay. Note that this field is not retained, after a DeepSleep reset, the tests should be re-started. This is because the true random number generator is active logic functionality.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						START_RC [1:1]	START_AP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	START_AP	RW	RW	0	Adaptive proportion (AP) test enable: '0': Stopped. '1': Started. On a AP detection, HW sets this field to '0' and sets INTR.TR_AP_DETECT to '1'.
1	START_RC	RW	RW	0	Repetition count (RC) test enable: '0': Disabled. '1': Enabled. On a RC detection, HW sets this field to '0' and sets INTR.TR_RC_DETECT to '1'.

6.1.27 CRYPTO_TR_MON_RC_CTL

Description: True random monitor RC control
Address: 0x401002D0
Offset: 0x2D0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUTOFF_COUNT8 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CUTOFF_COUNT8	RW	RW	255	Cutoff count (legal range is [1, 255]): '0': Illegal. '1': 1 repetition. ... '255': 255 repetitions.

6.1.28 CRYPTO_TR_MON_RC_STATUS0

Description: True random monitor RC status 0
Address: 0x401002D8
Offset: 0x2D8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							BIT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BIT	R	R	0	Current active bit value: '0': '0'. '1': '1'. This field is only valid when TR_MON_RC_STATUS1.REP_COUNT is NOT equal to '0'.

6.1.29 CRYPTO_TR_MON_RC_STATUS1

Description: True random monitor RC status 1
Address: 0x401002DC
Offset: 0x2DC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REP_COUNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	REP_COUNT	R	R	0	Number of repetitions of the current active bit counter: '0': 0 repetitions. ... '255': 255 repetitions.

6.1.30 CRYPTO_TR_MON_AP_CTL

Description: True random monitor AP control
Address: 0x401002E0
Offset: 0x2E0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUTOFF_COUNT16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CUTOFF_COUNT16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WINDOW_SIZE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WINDOW_SIZE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	CUTOFF_COUNT16	RW	RW	65535	Cutoff count (legal range is [1, 65535]). '0': Illegal. '1': 1 occurrence. ... '65535': 65535 occurrences.
16:31	WINDOW_SIZE	RW	RW	65535	Window size (minus 1) : '0': 1 bit. ... '65535': 65536 bits.

6.1.31 CRYPTO_TR_MON_AP_STATUS0

Description: True random monitor AP status 0
Address: 0x401002E8
Offset: 0x2E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							BIT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BIT	R	R	0	Current active bit value: '0': '0'. '1': '1'. This field is only valid when TR_MON_AP_STATUS1.OCC_COUNT is NOT equal to '0'.

6.1.32 CRYPTO_TR_MON_AP_STATUS1

Description: True random monitor AP status 1
Address: 0x401002EC
Offset: 0x2EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OCC_COUNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	OCC_COUNT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WINDOW_INDEX [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WINDOW_INDEX [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	OCC_COUNT	R	R	0	Number of occurrences of the current active bit counter: '0': 0 occurrences ... '65535': 65535 occurrences
16:31	WINDOW_INDEX	R	R	0	Counter to keep track of the current index in the window (counts from '0' to TR_MON_AP_CTL.WINDOW_SIZE to '0').

6.1.33 CRYPTO_STATUS

Description: Status
Address: 0x40101004
Offset: 0x1004
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	BUSY	R	R	0	Reflects the state of the IP: '0': Idle/no busy. '1': Busy: - Instruction is pending in the instruction FIFO. - Instruction is busy in a IP component (e.g. SHA1, SHA2, SHA3, DES, TDES, AES, CHACHA, ...). - Store FIFO is busy. - TR or PR command is busy.

6.1.34 CRYPTO_INSTR_FF_CTL

Description: Instruction FIFO control
Address: 0x40101040
Offset: 0x1040
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x20000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					EVENT_LEVEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						BLOCK [17:17]	CLEAR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	EVENT_LEVEL	RW	RW	0	Event level. When the number of entries in the instruction FIFO is less than the amount of this field, an event is generated: - 'event' = INSTR_FF_STATUS.USED < EVENT_LEVEL.
16	CLEAR	RW	RW	0	When '1', the instruction FIFO is cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period. HW sets this field to '1' on when a INSTR_OPC_ERROR, INSTR_CC_ERROR or BUS_ERROR interrupt cause is activated.
17	BLOCK	RW	RW	1	This field specifies the behavior when an instruction is written to a full FIFO (INSTR_FIFO_WR MMIO register): '0': The write is ignored/dropped and the INTR.INSTR_FF_OVERFLOW interrupt cause is set to '1'. '1': The write is blocked, resulting in AHB-Lite wait states and the INTR.INSTR_FF_OVERFLOW interrupt cause is set to '1' (this cause may be masked out). The instruction is written to the FIFO as soon as a FIFO entry becomes available. The maximum time is roughly the time of the execution of the slowest/longest instruction. Note that this setting may 'lock up' /stall the CPU. When the CPU is 'locked up'/stalled it can not respond to any system interrupts. As a result, the interrupt latency is increased. Note that this may not be an issue if the associated CPU is only performing cryptography functionality, e.g. the CM0+ during boot time.

6.1.35 CRYPTO_INSTR_FF_STATUS

Description: Instruction FIFO status
Address: 0x40101044
Offset: 0x1044
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				USED [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							EVENT [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	USED	R	R	0	Number of instructions in the instruction FIFO. The value of this field ranges from 0 to 8.
16	EVENT	R	R	0	Instruction FIFO event.

6.1.36 CRYPTO_INSTR_FF_WR

Description: Instruction FIFO write
Address: 0x40101048
Offset: 0x1048
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	W	W	0	Instruction or instruction operand data that is written to the instruction FIFO.

6.1.37 CRYPTO_LOAD0_FF_STATUS

Description: Load 0 FIFO status
Address: 0x401010C0
Offset: 0x10C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			USED5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	USED5	R	R	0	Number of Bytes in the FIFO. The value of this field is in the range [0, 19].
31	BUSY	R	R	0	Reflects the state of the FIFO: '0': FIFO load engine is idle and a new FIFO instruction can be accepted. '1': FIFO load engine is busy and NO new FIFO instruction can be accepted.

6.1.38 CRYPTO_LOAD1_FF_STATUS

Description: Load 1 FIFO status
Address: 0x401010D0
Offset: 0x10D0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			USED5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	USED5	R	R	0	See LOAD1_FF_STATUS.USED.
31	BUSY	R	R	0	See LOAD1_FF_STATUS.BUSY.

6.1.39 CRYPTO_STORE_FF_STATUS

Description: Store FIFO status
Address: 0x401010F0
Offset: 0x10F0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			USED5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	USED5	R	R	0	Number of Bytes in the FIFO. The value of this field is in the range [0, 16].
31	BUSY	R	R	0	Reflects the state of the FIFO: '0': FIFO store engine is idle and a new FIFO instruction can be accepted (USED is '0'). '1': FIFO store engine is busy and NO new FIFO instruction can be accepted.

6.1.40 CRYPTO_AES_CTL

Description: AES control
Address: 0x40101100
Offset: 0x1100
Retention: Retained
IsDeepSleep: No
Comment: The AES algorithm is compliant with FIPS 197.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						KEY_SIZE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	KEY_SIZE	RW	RW	0	AES key size: '0': 128-bit key, 10 rounds AES (inverse) cipher operation. '1': 192-bit key, 12 rounds AES (inverse) cipher operation. '2': 256-bit key, 14 rounds AES (inverse) cipher operation. '3': Undefined
	AES128			0	N/A
	AES192			1	N/A
	AES256			2	N/A

6.1.41 CRYPTO_RESULT

Description: Result
Address: 0x40101180
Offset: 0x1180
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	0	BLOCK_CMP operation (DATA[0]): '0': source 0 equals source 1. '1': source 0 does NOT equal source 1. CRC operation (DATA[31:0]). State of a 32-bit Linear Feedback Shift Registers (LFSR) that is used to implement CRC. This register needs to be initialized by SW to provide the CRC seed value. The seed value should be aligned such that the more significant bits (bit 31 and down) contain the seed value and the less significant bits (bit 0 and up) contain padding '0's. Note that SW can write this field. This functionality can be used prevent information leakage.

6.1.42 CRYPTO_CRC_CTL

Description: CRC control
Address: 0x40101400
Offset: 0x1400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							DATA_REVERSE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							REM_REVERSE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DATA_REVERSE	RW	RW	0	Specifies the bit order in which a data Byte is processed (reversal is performed after XORing): '0': Most significant bit (bit 1) first. '1': Least significant bit (bit 0) first.
8	REM_REVERSE	RW	RW	0	Specifies whether the remainder is bit reversed (reversal is performed after XORing): '0': No. '1': Yes.

6.1.43 CRYPTO_CRC_DATA_CTL

Description: CRC data control
Address: 0x40101410
Offset: 0x1410
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA_XOR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA_XOR	RW	RW	0	Specifies a byte mask with which each data byte is XOR'd. The XOR is performed before data reversal.

6.1.44 CRYPTO_CRC_POL_CTL

Description: CRC polynomial control
Address: 0x40101420
Offset: 0x1420
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	POLYNOMIAL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	POLYNOMIAL [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	POLYNOMIAL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	POLYNOMIAL [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	POLYNOMIAL	RW	RW	0	CRC polynomial. The polynomial is represented WITHOUT the high order bit (this bit is always assumed '1'). The polynomial should be aligned/shifted such that the more significant bits (bit 31 and down) contain the polynomial and the less significant bits (bit 0 and up) contain padding '0's. Some frequently used polynomials: - CRC32: POLYNOMIAL is 0x04c11db7 ($x^{32} + x^{26} + x^{23} + x^{22} + x^{16} + x^{12} + x^{11} + x^{10} + x^8 + x^7 + x^5 + x^4 + x^2 + x + 1$). - CRC16: POLYNOMIAL is 0x80050000 ($x^{16} + x^{15} + x^2 + 1$, shifted by 16 bit positions). - CRC16 CCITT: POLYNOMIAL is 0x10210000 ($x^{16} + x^{12} + x^5 + 1$, shifted by 16 bit positions).

6.1.45 CRYPTO_CRC_REM_CTL

Description: CRC remainder control
Address: 0x40101440
Offset: 0x1440
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REM_XOR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REM_XOR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REM_XOR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REM_XOR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REM_XOR	RW	RW	0	Specifies a mask with which the CRC_LFSR_CTL.LFSR32 register is XOR'd to produce a remainder. The XOR is performed before remainder reversal.

6.1.46 CRYPTO_CRC_REM_RESULT

Description: CRC remainder result
Address: 0x40101448
Offset: 0x1448
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REM	R	R	0	Remainder value. The alignment of the remainder depends on CRC_REM_CTL0.REM_REVERSE: '0': the more significant bits (bit 31 and down) contain the remainder. '1': the less significant bits (bit 0 and up) contain the remainder. Note: This field is combinatorially derived from CRC_LFSR_CTL.LFSR32, CRC_REM_CTL0.REM_REVERSE and CRC_REM_CTL1.REM_XOR.

6.1.47 CRYPTO_VU_CTL0

Description: Vector unit control 0
Address: 0x40101480
Offset: 0x1480
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ALWAYS_EXECUTE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALWAYS_EXECUTE	RW	RW	0	Specifies if a conditional instruction is executed or not, when its condition code evaluates to false/'0'. '0': The instruction is NOT executed. As a result, the instruction may be handled faster than when it is executed. '1': The instruction is executed, but the execution result (including status field information) is not reflected in the IP. The instruction is handled just as fast as when it is executed. Note: a conditional instruction with a condition code that evaluates to false/'0' does not affect the architectural state: VU_STATUS fields, memory or register-file data. Note: Always execution is useful to prevent/complicate differential timing and differential power attacks.

6.1.48 CRYPTO_VU_CTL1

Description: Vector unit control 1
Address: 0x40101484
Offset: 0x1484
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR24 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR24 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR24 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:31	ADDR24	RW	RW	0	Specifies the memory address for the vector unit operand memory region. The register-file registers provide 13-bit word offsets within this memory region. Given ADDR[31:8], VU_VTL2.MASK[14:8] and a 13-bit word offset offset[14:2], a vector operand memory address VU_OPERAND_ADDR[31:0] is calculated as follows: - VU_OPERAND_ADDR[31:15] = ADDR[31:15] - VU_OPERAND_ADDR[14:8] = (ADDR[14:8] & MASK[14:8]) (offset[14:8] & ~MASK[14:8]) - VU_OPERAND_ADDR[7:2] = offset[7:2] - VU_OPERAND_ADDR[1:0] = 0 (always word aligned) The vector unit operand memory region uses either the IP's memory buffer or system memory. For best performance, the IP's memory buffer should be used and ADDR should be set to MEM_BUFF and MASK should specify the IP memory buffer size. If a vector operand memory address is mapped on a memory hole, read accesses return a '0' and write accesses are ignored.

6.1.49 CRYPTO_VU_CTL2

Description: Vector unit control 2
Address: 0x40101488
Offset: 0x1488
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x7F00

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	MASK [14:8]						

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:14	MASK	RW	RW	127	Specifies the size of the vector operand memory region. Legal values: '0b0000000': 32 KB memory region (VU_VTL1.ADDR[14:8] ignored). '0b1000000': 16 KB memory region (VU_VTL1.ADDR[13:8] ignored). '0b1100000': 8 KB memory region (VU_VTL1.ADDR[12:8] ignored). '0b1110000': 4 KB memory region (VU_VTL1.ADDR[11:8] ignored). '0b1111000': 2 KB memory region (VU_VTL1.ADDR[10:8] ignored). '0b1111100': 1 KB memory region (VU_VTL1.ADDR[9:8] ignored). '0b1111110': 512 B memory region (VU_VTL1.ADDR[8] ignored). '0b1111111': 256 B memory region. Note: the default specifies a 256 B memory region.

6.1.50 CRYPTO_VU_STATUS

Description: Vector unit status
Address: 0x40101490
Offset: 0x1490
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				ONE [3:3]	ZERO [2:2]	EVEN [1:1]	CARRY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CARRY	R	R	0	STATUS CARRY field.
1	EVEN	R	R	0	STATUS EVEN field.
2	ZERO	R	R	0	STATUS ZERO field.
3	ONE	R	R	0	STATUS ONE field.

6.1.51 CRYPTO_VU_RF_DATA

Description: Vector unit register-file
Address: 0x401014C0
Offset: 0x14C0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	R	R	0	Vector unit register-file data. A register-file register has the following layout: DATA[28:16]: data (typically used as a word offset in vector unit operand memory). DATA[12:0]: bit size minus 1.

6.1.52 CRYPTO_DEV_KEY_ADDR0_CTL

Description: Device key address 0 control

Address: 0x40102000

Offset: 0x2000

Retention: Retained

IsDeepSleep: No

Comment: The DEV_KEY_ADDR0/1_CTL and DEV_KEY_ADDR0/1 register are typically supported by a per fixed protection structure pair.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	RW	RW	0	Specifies if the address in the associated DEV_KEY_ADDR0 is valid: '0': Address not valid; i.e. no device key specified. '1': Address valid; i.e. device key specified. Note: A LOAD_DEV_KEY instruction requires that the device key's valid field is '1'.

6.1.53 CRYPTO_DEV_KEY_ADDR0

Description: Device key address 0
Address: 0x40102004
Offset: 0x2004
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR32	RW	RW	0	Specifies the memory address of the device key in memory. A LOAD_DEV_KEY instruction uses this address to load a device key from memory into the IP register buffer blocks 4 and 5.

6.1.54 CRYPTO_DEV_KEY_ADDR1_CTL

Description: Device key address 1 control
Address: 0x40102020
Offset: 0x2020
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	RW	RW	0	See DEV_KEY_ADDR0_CTL.

6.1.55 CRYPTO_DEV_KEY_ADDR1

Description: Device key address 1 control
Address: 0x40102024
Offset: 0x2024
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR32	RW	RW	0	See DEV_KEY_ADDR0.

6.1.56 CRYPTO_DEV_KEY_STATUS

Description: Device key status
Address: 0x40102080
Offset: 0x2080
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							LOADED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOADED	R	R	0	Specifies if a device key is present in the IP register buffer blocks 4 and 5. HW sets this field to '1' on successful completion of a LOAD_DEV_KEY instruction. HW clears this field to '0' when a CLEAR instruction is executed (the CLEAR instruction also sets the IP register buffer to '0').

6.1.57 CRYPTO_DEV_KEY_CTL0

Description: Device key control 0
Address: 0x40102100
Offset: 0x2100
Retention: Not Retained
IsDeepSleep: No
Comment: This register is typically supported by a peri fixed protection structure pair.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ALLOWED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALLOWED	RW	RW	0	Specifies if a LOAD_DEV_KEY instruction is allowed to use the device key in memory: '0': Not allowed. '1': Allowed. Note: For successful completion of a LOAD_DEV_KEY instruction, both the associated DEV_KEY_ADDR_CTL.VALID and DEV_KEY_CTL.ALLOWED fields must be '1'. On successful instruction completion, DEV_KEY_STATUS.LOADED is set to '1'. On unsuccessful completion, the instruction FIFO is cleared and the IP is locked; an Active reset or an IP reset (CTL.ENABLED), which reinitializes the IP, is required. Note: A LOAD_DEV_KEY loads the device key from memory with protection context '0'.

6.1.58 CRYPTO_DEV_KEY_CTL1

Description: Device key control 1
Address: 0x40102120
Offset: 0x2120
Retention: Not Retained
IsDeepSleep: No
Comment: This register is typically supported by a peri fixed protection structure pair.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ALLOWED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ALLOWED	RW	RW	0	See DEV_KEY_CTL0.

6.1.59 CRYPTO_MEM_BUFF

Description: Memory buffer

Address: 0x40108000

Offset: 0x8000

Retention: Retained

IsDeepSleep: No

Comment: The memory buffer is used to hold operand data. The buffer can have a capacity of 256 B, 512 B, 1 KB, 2 KB, 4 KB, 8 KB, 16 KB or 32 KB (up to 8192 32-bit Words).

SW may access the memory buffer during an instruction that operates on operands in the memory buffer. This allows SW data movement to and from the memory buffer to overlap with IP execution on memory buffer data. Note: SW should not modify memory buffer operand data of the busy instruction.

The memory buffer can be accessed with 8-bit, 16-bit and 32-bit AHB-Lite transfers.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	Undefined	N/A

7 DMAC

Description	DMAC
Base Address	0x402A0000
Size	0x10000
Slave Num	MMIO2 - 9

Register Name	Address	Permission	Description
DMAC_CTL	0x402A0000	FULL	Control
DMAC_ACTIVE	0x402A0008	FULL	Active channels

7.1 CH 0

Register Name	Address	Permission	Description
DMAC_CH0_CTL	0x402A1000	FULL	Channel control
DMAC_CH0_IDX	0x402A1010	FULL	Channel current indices
DMAC_CH0_SRC	0x402A1014	FULL	Channel current source address
DMAC_CH0_DST	0x402A1018	FULL	Channel current destination address
DMAC_CH0_CURR	0x402A1020	FULL	Channel current descriptor pointer
DMAC_CH0_TR_CMD	0x402A1028	FULL	Channel software trigger
DMAC_CH0_DESCR_STATUS	0x402A1040	FULL	Channel descriptor status
DMAC_CH0_DESCR_CTL	0x402A1060	FULL	Channel descriptor control
DMAC_CH0_DESCR_SRC	0x402A1064	FULL	Channel descriptor source
DMAC_CH0_DESCR_DST	0x402A1068	FULL	Channel descriptor destination
DMAC_CH0_DESCR_X_SIZE	0x402A106C	FULL	Channel descriptor X size
DMAC_CH0_DESCR_X_INCR	0x402A1070	FULL	Channel descriptor X increment
DMAC_CH0_DESCR_Y_SIZE	0x402A1074	FULL	Channel descriptor Y size
DMAC_CH0_DESCR_Y_INCR	0x402A1078	FULL	Channel descriptor Y increment
DMAC_CH0_DESCR_NEXT	0x402A107C	FULL	Channel descriptor next pointer
DMAC_CH0_INTR	0x402A1080	FULL	Interrupt
DMAC_CH0_INTR_SET	0x402A1084	FULL	Interrupt set
DMAC_CH0_INTR_MASK	0x402A1088	FULL	Interrupt mask
DMAC_CH0_INTR_MASKED	0x402A108C	FULL	Interrupt masked

7.2 CH 1

Register Name	Address	Permission	Description
DMAC_CH1_CTL	0x402A1100	FULL	Channel control
DMAC_CH1_IDX	0x402A1110	FULL	Channel current indices
DMAC_CH1_SRC	0x402A1114	FULL	Channel current source address
DMAC_CH1_DST	0x402A1118	FULL	Channel current destination address
DMAC_CH1_CURR	0x402A1120	FULL	Channel current descriptor pointer
DMAC_CH1_TR_CMD	0x402A1128	FULL	Channel software trigger
DMAC_CH1_DESCR_STATUS	0x402A1140	FULL	Channel descriptor status
DMAC_CH1_DESCR_CTL	0x402A1160	FULL	Channel descriptor control
DMAC_CH1_DESCR_SRC	0x402A1164	FULL	Channel descriptor source
DMAC_CH1_DESCR_DST	0x402A1168	FULL	Channel descriptor destination
DMAC_CH1_DESCR_X_SIZE	0x402A116C	FULL	Channel descriptor X size
DMAC_CH1_DESCR_X_INCR	0x402A1170	FULL	Channel descriptor X increment
DMAC_CH1_DESCR_Y_SIZE	0x402A1174	FULL	Channel descriptor Y size
DMAC_CH1_DESCR_Y_INCR	0x402A1178	FULL	Channel descriptor Y increment
DMAC_CH1_DESCR_NEXT	0x402A117C	FULL	Channel descriptor next pointer
DMAC_CH1_INTR	0x402A1180	FULL	Interrupt
DMAC_CH1_INTR_SET	0x402A1184	FULL	Interrupt set
DMAC_CH1_INTR_MASK	0x402A1188	FULL	Interrupt mask
DMAC_CH1_INTR_MASKED	0x402A118C	FULL	Interrupt masked

7.3 CH 2

Register Name	Address	Permission	Description
DMAC_CH2_CTL	0x402A1200	FULL	Channel control
DMAC_CH2_IDX	0x402A1210	FULL	Channel current indices
DMAC_CH2_SRC	0x402A1214	FULL	Channel current source address
DMAC_CH2_DST	0x402A1218	FULL	Channel current destination address
DMAC_CH2_CURR	0x402A1220	FULL	Channel current descriptor pointer

Register Name	Address	Permission	Description
DMAC_CH2_TR_CMD	0x402A1228	FULL	Channel software trigger
DMAC_CH2_DESCR_STATUS	0x402A1240	FULL	Channel descriptor status
DMAC_CH2_DESCR_CTL	0x402A1260	FULL	Channel descriptor control
DMAC_CH2_DESCR_SRC	0x402A1264	FULL	Channel descriptor source
DMAC_CH2_DESCR_DST	0x402A1268	FULL	Channel descriptor destination
DMAC_CH2_DESCR_X_SIZE	0x402A126C	FULL	Channel descriptor X size
DMAC_CH2_DESCR_X_INCR	0x402A1270	FULL	Channel descriptor X increment
DMAC_CH2_DESCR_Y_SIZE	0x402A1274	FULL	Channel descriptor Y size
DMAC_CH2_DESCR_Y_INCR	0x402A1278	FULL	Channel descriptor Y increment
DMAC_CH2_DESCR_NEXT	0x402A127C	FULL	Channel descriptor next pointer
DMAC_CH2_INTR	0x402A1280	FULL	Interrupt
DMAC_CH2_INTR_SET	0x402A1284	FULL	Interrupt set
DMAC_CH2_INTR_MASK	0x402A1288	FULL	Interrupt mask
DMAC_CH2_INTR_MASKED	0x402A128C	FULL	Interrupt masked

7.4 CH 3

Register Name	Address	Permission	Description
DMAC_CH3_CTL	0x402A1300	FULL	Channel control
DMAC_CH3_IDX	0x402A1310	FULL	Channel current indices
DMAC_CH3_SRC	0x402A1314	FULL	Channel current source address
DMAC_CH3_DST	0x402A1318	FULL	Channel current destination address
DMAC_CH3_CURR	0x402A1320	FULL	Channel current descriptor pointer
DMAC_CH3_TR_CMD	0x402A1328	FULL	Channel software trigger
DMAC_CH3_DESCR_STATUS	0x402A1340	FULL	Channel descriptor status
DMAC_CH3_DESCR_CTL	0x402A1360	FULL	Channel descriptor control
DMAC_CH3_DESCR_SRC	0x402A1364	FULL	Channel descriptor source
DMAC_CH3_DESCR_DST	0x402A1368	FULL	Channel descriptor destination
DMAC_CH3_DESCR_X_SIZE	0x402A136C	FULL	Channel descriptor X size
DMAC_CH3_DESCR_X_INCR	0x402A1370	FULL	Channel descriptor X increment
DMAC_CH3_DESCR_Y_SIZE	0x402A1374	FULL	Channel descriptor Y size
DMAC_CH3_DESCR_Y_INCR	0x402A1378	FULL	Channel descriptor Y increment
DMAC_CH3_DESCR_NEXT	0x402A137C	FULL	Channel descriptor next pointer
DMAC_CH3_INTR	0x402A1380	FULL	Interrupt
DMAC_CH3_INTR_SET	0x402A1384	FULL	Interrupt set
DMAC_CH3_INTR_MASK	0x402A1388	FULL	Interrupt mask
DMAC_CH3_INTR_MASKED	0x402A138C	FULL	Interrupt masked

7.5 CH 4

Register Name	Address	Permission	Description
DMAC_CH4_CTL	0x402A1400	FULL	Channel control
DMAC_CH4_IDX	0x402A1410	FULL	Channel current indices
DMAC_CH4_SRC	0x402A1414	FULL	Channel current source address
DMAC_CH4_DST	0x402A1418	FULL	Channel current destination address
DMAC_CH4_CURR	0x402A1420	FULL	Channel current descriptor pointer
DMAC_CH4_TR_CMD	0x402A1428	FULL	Channel software trigger
DMAC_CH4_DESCR_STATUS	0x402A1440	FULL	Channel descriptor status
DMAC_CH4_DESCR_CTL	0x402A1460	FULL	Channel descriptor control
DMAC_CH4_DESCR_SRC	0x402A1464	FULL	Channel descriptor source
DMAC_CH4_DESCR_DST	0x402A1468	FULL	Channel descriptor destination
DMAC_CH4_DESCR_X_SIZE	0x402A146C	FULL	Channel descriptor X size
DMAC_CH4_DESCR_X_INCR	0x402A1470	FULL	Channel descriptor X increment
DMAC_CH4_DESCR_Y_SIZE	0x402A1474	FULL	Channel descriptor Y size
DMAC_CH4_DESCR_Y_INCR	0x402A1478	FULL	Channel descriptor Y increment
DMAC_CH4_DESCR_NEXT	0x402A147C	FULL	Channel descriptor next pointer
DMAC_CH4_INTR	0x402A1480	FULL	Interrupt
DMAC_CH4_INTR_SET	0x402A1484	FULL	Interrupt set
DMAC_CH4_INTR_MASK	0x402A1488	FULL	Interrupt mask
DMAC_CH4_INTR_MASKED	0x402A148C	FULL	Interrupt masked

7.6 CH 5

Register Name	Address	Permission	Description
DMAC_CH5_CTL	0x402A1500	FULL	Channel control
DMAC_CH5_IDX	0x402A1510	FULL	Channel current indices
DMAC_CH5_SRC	0x402A1514	FULL	Channel current source address
DMAC_CH5_DST	0x402A1518	FULL	Channel current destination address
DMAC_CH5_CURR	0x402A1520	FULL	Channel current descriptor pointer
DMAC_CH5_TR_CMD	0x402A1528	FULL	Channel software trigger
DMAC_CH5_DESCR_STATUS	0x402A1540	FULL	Channel descriptor status
DMAC_CH5_DESCR_CTL	0x402A1560	FULL	Channel descriptor control
DMAC_CH5_DESCR_SRC	0x402A1564	FULL	Channel descriptor source
DMAC_CH5_DESCR_DST	0x402A1568	FULL	Channel descriptor destination
DMAC_CH5_DESCR_X_SIZE	0x402A156C	FULL	Channel descriptor X size
DMAC_CH5_DESCR_X_INCR	0x402A1570	FULL	Channel descriptor X increment
DMAC_CH5_DESCR_Y_SIZE	0x402A1574	FULL	Channel descriptor Y size
DMAC_CH5_DESCR_Y_INCR	0x402A1578	FULL	Channel descriptor Y increment
DMAC_CH5_DESCR_NEXT	0x402A157C	FULL	Channel descriptor next pointer
DMAC_CH5_INTR	0x402A1580	FULL	Interrupt
DMAC_CH5_INTR_SET	0x402A1584	FULL	Interrupt set
DMAC_CH5_INTR_MASK	0x402A1588	FULL	Interrupt mask
DMAC_CH5_INTR_MASKED	0x402A158C	FULL	Interrupt masked

7.7 CH 6

Register Name	Address	Permission	Description
DMAC_CH6_CTL	0x402A1600	FULL	Channel control
DMAC_CH6_IDX	0x402A1610	FULL	Channel current indices
DMAC_CH6_SRC	0x402A1614	FULL	Channel current source address
DMAC_CH6_DST	0x402A1618	FULL	Channel current destination address
DMAC_CH6_CURR	0x402A1620	FULL	Channel current descriptor pointer
DMAC_CH6_TR_CMD	0x402A1628	FULL	Channel software trigger
DMAC_CH6_DESCR_STATUS	0x402A1640	FULL	Channel descriptor status
DMAC_CH6_DESCR_CTL	0x402A1660	FULL	Channel descriptor control
DMAC_CH6_DESCR_SRC	0x402A1664	FULL	Channel descriptor source
DMAC_CH6_DESCR_DST	0x402A1668	FULL	Channel descriptor destination
DMAC_CH6_DESCR_X_SIZE	0x402A166C	FULL	Channel descriptor X size
DMAC_CH6_DESCR_X_INCR	0x402A1670	FULL	Channel descriptor X increment
DMAC_CH6_DESCR_Y_SIZE	0x402A1674	FULL	Channel descriptor Y size
DMAC_CH6_DESCR_Y_INCR	0x402A1678	FULL	Channel descriptor Y increment
DMAC_CH6_DESCR_NEXT	0x402A167C	FULL	Channel descriptor next pointer
DMAC_CH6_INTR	0x402A1680	FULL	Interrupt
DMAC_CH6_INTR_SET	0x402A1684	FULL	Interrupt set
DMAC_CH6_INTR_MASK	0x402A1688	FULL	Interrupt mask
DMAC_CH6_INTR_MASKED	0x402A168C	FULL	Interrupt masked

7.8 CH 7

Register Name	Address	Permission	Description
DMAC_CH7_CTL	0x402A1700	FULL	Channel control
DMAC_CH7_IDX	0x402A1710	FULL	Channel current indices
DMAC_CH7_SRC	0x402A1714	FULL	Channel current source address
DMAC_CH7_DST	0x402A1718	FULL	Channel current destination address
DMAC_CH7_CURR	0x402A1720	FULL	Channel current descriptor pointer
DMAC_CH7_TR_CMD	0x402A1728	FULL	Channel software trigger
DMAC_CH7_DESCR_STATUS	0x402A1740	FULL	Channel descriptor status
DMAC_CH7_DESCR_CTL	0x402A1760	FULL	Channel descriptor control
DMAC_CH7_DESCR_SRC	0x402A1764	FULL	Channel descriptor source
DMAC_CH7_DESCR_DST	0x402A1768	FULL	Channel descriptor destination
DMAC_CH7_DESCR_X_SIZE	0x402A176C	FULL	Channel descriptor X size
DMAC_CH7_DESCR_X_INCR	0x402A1770	FULL	Channel descriptor X increment
DMAC_CH7_DESCR_Y_SIZE	0x402A1774	FULL	Channel descriptor Y size
DMAC_CH7_DESCR_Y_INCR	0x402A1778	FULL	Channel descriptor Y increment
DMAC_CH7_DESCR_NEXT	0x402A177C	FULL	Channel descriptor next pointer
DMAC_CH7_INTR	0x402A1780	FULL	Interrupt
DMAC_CH7_INTR_SET	0x402A1784	FULL	Interrupt set
DMAC_CH7_INTR_MASK	0x402A1788	FULL	Interrupt mask

Register Name	Address	Permission	Description
DMAC_CH7_INTR_MASKED	0x402A178C	FULL	Interrupt masked

7.9 Register Details

7.9.1 DMAC_CTL

Description: Control
Address: 0x402A0000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLED	RW	RW	0	IP enable: '0': Disabled. All non-retention registers (command and status registers) are reset to their default value when the IP is disabled. All retention registers retain their value when the IP is disabled. '1': Enabled.
	DISABLED			0	N/A
	ENABLED			1	N/A

7.9.2 DMAC_ACTIVE

Description: Active channels
Address: 0x402A0008
Offset: 0x8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ACTIVE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ACTIVE	R	R	0	Specifies active channels; i.e. enabled channels whose trigger got activated.

7.9.3 CH

7.9.3.1 DMAC_CH_CTL

Description: Channel control
Address: 0x402A1000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:3]	B [2:2]	NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	0	User/privileged access control: '0': user mode. '1': privileged mode. This field is set with the user/privileged access control of the transaction that writes this register; i.e. the access control is inherited from the write transaction and not specified by the transaction write data. All transactions for this channel use the P field for the user/privileged access control ('hprot[1]').
1	NS	RW	RW	1	Secure/on-secure access control: '0': secure. '1': non-secure. This field is set with the secure/non-secure access control of the transaction that writes this register; i.e. the access control is inherited from the write transaction and not specified by the transaction write data. All transactions for this channel use the NS field for the secure/non-secure access control ('hprot[4]').
2	B	RW	RW	0	Non-bufferable/bufferable access control: '0': non-bufferable. '1': bufferable. This field is used to indicate to an AMBA bridge that a write transaction can complete without waiting for the destination to accept the write transaction data. All transactions for this channel uses the B field for the non-bufferable/bufferable access control ('hprot[2]').

Bits	Name	SW	HW	Default or Enum	Description
4:7	PC	RW	RW	0	Protection context. This field is set with the protection context of the transaction that writes this register; i.e. the context is inherited from the write transaction and not specified by the transaction write data. All transactions for this channel uses the PC field for the protection context.
8:9	PRI0	RW	RW	0	Channel priority: '0': highest priority. '1' '2' '3': lowest priority. Channels with the same priority constitute a priority group and within this priority group, the following 'roundrobin' arbitration is applied. A 'round' consists of a contiguous sequence of channel activations, within this priority group, without any repetition. Within a round, higher priority is given to the lower channel indices. The notion of a round guarantees that within a group, higher channel indices do not yield to lower indices indefinitely.
31	ENABLED	RW	RW	0	Channel enable: '0': Disabled. The channel's trigger is ignored and the channel cannot be made pending and therefore cannot be made active. If a pending channel is disabled, the channel is made non pending. If the activate channel is disabled, the channel is de-activated (bus transactions are completed). '1': Enabled. SW sets this field to '1' to enable a specific channel. HW sets this field to '0' when an error interrupt cause is activated.

7.9.3.2 DMAC_CH_IDX

Description: Channel current indices
Address: 0x402A1010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	X [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	X [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	Y [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	Y [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	X	R	R	Undefined	Specifies the X loop index. In the range of [0, X_COUNT], with X_COUNT taken from the current descriptor. Note: HW sets this field to '0' when it loads a descriptor.
16:31	Y	R	R	Undefined	Specifies the Y loop index, with Y_COUNT taken from the current descriptor. Note: HW sets this field to '0' when it loads a descriptor..

7.9.3.3 DMAC_CH_SRC

Description: Channel current source address
Address: 0x402A1014
Offset: 0x14
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	R	R	Undefined	Current address of source location.

7.9.3.4 DMAC_CH_DST

Description: Channel current destination address
Address: 0x402A1018
Offset: 0x18
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	R	R	Undefined	Current address of destination location.

7.9.3.5 DMAC_CH_CURR

Description: Channel current descriptor pointer
Address: 0x402A1020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	PTR	RW	RW	Undefined	Address of current descriptor. When this field is '0', there is no valid descriptor. Note: HW updates the current descriptor pointer CH_CURR_PTR with DESCR_NEXT_PTR after execution of the current descriptor.

7.9.3.6 DMAC_CH_TR_CMD

Description: Channle software trigger
Address: 0x402A1028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ACTIVATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ACTIVATE	RW1S	RW1S	0	Software trigger. When written with '1', a trigger is generated which sets 'trigger pending' (only if the channel is enabled). A read always returns a 0.

7.9.3.7 DMAC_CH_DESCR_STATUS

Description: Channel descriptor status
Address: 0x402A1040
Offset: 0x40
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	R	R	0	Indicates whether the descriptor information present in DESCR_CTL, DESCR_SRC, DESCR_DST, DESCR_X_SIZE, DESCR_X_INCR, DESCR_Y_SIZE, DESCR_Y_INCR, DESCR_NEXT status registers is valid or not.

7.9.3.8 DMAC_CH_DESCR_CTL

Description: Channel descriptor control
Address: 0x402A1060
Offset: 0x60
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_CTL of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TR_IN_TYPE [7:6]		TR_OUT_TYPE [5:4]		INTR_TYPE [3:2]		WAIT_FOR_DEACT [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							DATA_PREFETCH [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						DATA_SIZE [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	DESCR_TYPE [30:28]			DST_TRANS_FER_SIZE [27:27]	SRC_TRANS_FER_SIZE [26:26]	None [25:25]	CH_DISABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	WAIT_FOR_DEACT	R	R	Undefined	Specifies whether the controller should wait for the input trigger to be deactivated; i.e. the selected system trigger is not active. This field is used to synchronize the controller with the agent that generated the trigger. This field is ONLY used at the completion of the transfer as specified by TR_IN. E.g., a TX FIFO indicates that it is empty and it needs a new data sample. The agent removes the trigger ONLY when the data sample has been written by the controller AND received by the agent. Furthermore, the agent's trigger may be delayed by a few cycles before it reaches the controller. This field is used for level sensitive trigger, which reflect state (pulse sensitive triggers should have this field set to '0'). The wait cycles incurred by this field reduce DW controller performance. '0': Do not wait for trigger de-activation (for pulse sensitive triggers). '1': Wait for up to 4 cycles. '2': Wait for up to 16 cycles. '3': Wait indefinitely. This option may result in controller lockup if the trigger is not de-activated.

Bits	Name	SW	HW	Default or Enum	Description
2:3	INTR_TYPE	R	R	Undefined	Specifies when a completion interrupt is generated (CH_STATUS.INTR_CAUSE is set to COMPLETION): '0': An interrupt is generated after a single transfer. '1': An interrupt is generated after a single 1D transfer or a memory copy transfer - If the descriptor type is 'single', the interrupt is generated after a single transfer. - If the descriptor type is '1D' or '2D', the interrupt is generated after the execution of a 1D transfer. - If the descriptor type is 'memory copy', the interrupt is generated after the execution of a memory copy transfer. - If the descriptor type is 'scatter' the interrupt is generated after the execution of a scatter transfer. '2': An interrupt is generated after the execution of the current descriptor (independent of the value of DESCR_NEXT_PTR.ADDR of the current descriptor). '3': An interrupt is generated after the execution of the current descriptor and the current descriptor's DESCR_NEXT_PTR.ADDR is '0'.
4:5	TR_OUT_TYPE	R	R	Undefined	Specifies when an output trigger is generated: '0': An output trigger is generated after a single transfer. '1': An output trigger is generated after a single 1D transfer or a memory copy transfer. - If the descriptor type is 'single', the output trigger is generated after a single transfer. - If the descriptor type is '1D' or '2D', the output trigger is generated after the execution of a 1D transfer. - If the descriptor type is 'memory copy', the output trigger is generated after the execution of a memory copy transfer. - If the descriptor type is 'scatter', the output trigger is generated after the execution of a scatter transfer. '2': An output trigger is generated after the execution of the current descriptor. '3': An output trigger is generated after the execution of a descriptor list: after the execution of the current descriptor AND the current descriptor's DESCR_NEXT_PTR.ADDR is '0'.
6:7	TR_IN_TYPE	R	R	Undefined	Specifies the input trigger type (not to be confused with the descriptor type): '0': A trigger results in the execution of a single transfer. The descriptor type can be single, 1D or 2D. '1': A trigger results in the execution of a single 1D transfer. - If the descriptor type is 'single', the trigger results in the execution of a single transfer. - If the descriptor type is '1D' or '2D', the trigger results in the execution of a 1D transfer. - If the descriptor type is 'memory copy', the trigger results in the execution of a memory copy transfer. - If the descriptor type is 'scatter', the trigger results in the execution of an scatter transfer. '2': A trigger results in the execution of the current descriptor. '3': A trigger results in the execution of the current descriptor and continues (without requiring another input trigger) with the execution of the next descriptor using the next descriptor's information.

Bits	Name	SW	HW	Default or Enum	Description
8	DATA_PREFETCH	R	R	Undefined	Source data prefetch: '0': No source data prefetch. Source data transfers are only initiated AFTER the input trigger is activated. '1': Source data prefetch. Source data transfers are initiated as soon as the channel is enabled, the current descriptor pointer is NOT '0' and there is space available in the channel's data FIFO. When the input trigger is activated, the trigger can initiate destination data transfers with data that is already in the channel's data FIFO. This effectively shortens the initial delay of the data transfer. Note: data prefetch should be used with care, to ensure that data coherency is guaranteed and that prefetches do not cause undesired side effects.
16:17	DATA_SIZE	R	R	Undefined	Specifies the data element size: '0': Byte (8 bits). '1': Halfword (16 bits). '2': Word (32 bits). DATA_SIZE, SRC_TRANSFER_SIZE and DST_TRANSFER_SIZE together determine how data elements are transferred. The following are the 9 legal settings: - DATA is 8 bit, SRC is 8 bit, DST is 8 bit. - DATA is 8 bit, SRC is 32 bit (higher 24 bits are dropped), DST is 8 bit. - DATA is 8 bit, SRC is 8 bit, DST is 32 bit (higher 24 bits are made '0'). - DATA is 8 bit, SRC is 32 bit (higher 24 bits are dropped), DST is 32 bit (higher 24 bits are made '0'). - DATA is 16 bit, SRC is 16 bit, DST is 16 bit. - DATA is 16 bit, SRC is 32 bit (higher 16 bits are dropped), DST is 16 bit. - DATA is 16 bit, SRC is 16 bit, DST is 32 bit (higher 16 bits are made '0'). - DATA is 16 bit, SRC is 32 bit (higher 16 bits are dropped), DST is 32 bit (higher 16 bits are made '0'). - DATA is 32 bit, SRC is 32 bit, DST is 32 bit. Note: this field is not used for a 'memory copy' descriptor type. Note: this field must be set to '2' for a 'initialization' descriptor type.
24	CH_DISABLE	R	R	Undefined	Specifies whether the channel is disabled or not after completion of the current descriptor (independent of the value of the DESCR_NEXT_PTR value): '0': Channel is not disabled. '1': Channel is disabled.
26	SRC_TRANSFER_SIZE	R	R	Undefined	Specifies the bus transfer size to the source location: '0': As specified by DATA_SIZE. '1': Word (32 bits). Distinguishing bus transfer size from data element size allows for source components with data elements that are smaller than their 32-bit bus interface width. E.g., an ADC source has a 32-bit bus transfer size, but only provides a 16-bit data element. Note: this field is not used for a 'memory copy' descriptor type. Note: this field must be set to '1' for a 'scatter' descriptor type.

Bits	Name	SW	HW	Default or Enum	Description
27	DST_TRANSFER_SIZE	R	R	Undefined	Specifies the bus transfer size to the destination location: '0': As specified by DATA_SIZE. '1': Word (32 bits). Distinguishing bus transfer size from data element size allows for destination components with data elements that are smaller than their 32-bit bus interface width. E.g., a DAC destination has a 32-bit bus transfer size, but only requires a 16-bit data element. Note: this field is not used for a 'memory copy' descriptor type. Note: this field must be set to '1' for a 'scatter' descriptor type.
28:30	DESCR_TYPE	R	R	Undefined	Specifies the descriptor type (not to be confused with the trigger type): '0': Single transfer. The DESCR_X_SIZE, DESCR_X_INCR, DESCR_Y_SIZE and DESCR_Y_INCR registers are NOT present. The DESCR_NEXT_PTR is at offset 0x0c. '1': 1D transfer. The DESCR_X_SIZE and DESCR_X_INCR registers are present, the DESCR_Y_SIZE and DESCR_Y_INCR are NOT present. A 1D transfer consists out of DESCR_X_SIZE.X_COUNT+1 single transfers. The DESCR_NEXT_PTR is at offset 0x14. '2': 2D transfer. The DESCR_X_SIZE, DESCR_X_INCR, DESCR_Y_SIZE and DESCR_Y_INCR registers are present. A 2D transfer consists of (DESCR_X_SIZE.X_COUNT+1)* (DESCR_Y_SIZE.Y_COUNT+1) single transfers. The DESCR_NEXT_PTR is at offset 0x1c. '3': Memory copy. The DESCR_X_SIZE register is present, the DESCR_X_INCR, DESCR_Y_SIZE and DESCR_Y_INCR are NOT present. A memory copy transfer copies DESCR_X_SIZE.X_COUNT+1 Bytes and may use Byte, halfword and word transfers. The DESCR_NEXT_PTR is at offset 0x10. '4': Scatter transfer. The DESCR_X_SIZE register is present, the DESCR_DST, DESCR_X_INCR, DESCR_Y_SIZE and DESCR_Y_INCR are NOT present. '5'-7': Undefined. After the execution of the current descriptor, the DESCR_NEXT_PTR address is copied to the channel's CH_CURR_PTR address and CH_STATUS.X_IDX and CH_STATUS.Y_IDX are set to '0'.

7.9.3.9 DMAC_CH_DESCR_SRC

Description: Channel descriptor source
Address: 0x402A1064
Offset: 0x64
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_SRC of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	R	R	Undefined	Base address of source location.

7.9.3.10 DMAC_CH_DESCR_DST

Description: Channel descriptor destination
Address: 0x402A1068
Offset: 0x68
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_DST of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDR	R	R	Undefined	Base address of destination location.

7.9.3.11 DMAC_CH_DESCR_X_SIZE

Description: Channel descriptor X size
Address: 0x402A106C
Offset: 0x6C
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_X_SIZE of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	X_COUNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	X_COUNT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	X_COUNT	R	R	Undefined	Number of iterations (minus 1) of the 'X loop' (X_COUNT+1 is the number of single transfers in a 1D transfer). This field is an unsigned number in the range [0, 65535], representing 1 through 65536 iterations. For the 'memory copy' descriptor type, (X_COUNT + 1) is the number of transferred Bytes. For the 'scatter' descriptor type, ceiling(X_COUNT/2) is the number of (address, write data) initialization pairs processed.

7.9.3.12 DMAC_CH_DESCR_X_INCR

Description: Channel descriptor X increment
Address: 0x402A1070
Offset: 0x70
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_X_INCR of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SRC_X [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SRC_X [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DST_X [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DST_X [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	SRC_X	R	R	Undefined	Specifies increment of source address for each X loop iteration (in multiples of SRC_TRANSFER_SIZE). This field is a signed number (sign-magnitude format) in the range [-32768, 32767]. If this field is '0', the source address is not incremented. This is useful for reading from RX FIFO structures.
16:31	DST_X	R	R	Undefined	Specifies increment of destination address for each X loop iteration (in multiples of DST_TRANSFER_SIZE). This field is a signed number (sign-magnitude format) in the range [-32768, 32767]. If this field is '0', the destination address is not incremented. This is useful for writing to TX FIFO structures.

7.9.3.13 DMAC_CH_DESCR_Y_SIZE

Description: Channel descriptor Y size
Address: 0x402A1074
Offset: 0x74
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_Y_SIZE of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	Y_COUNT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	Y_COUNT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	Y_COUNT	R	R	Undefined	Number of iterations (minus 1) of the 'Y loop' (X_COUNT+1)*(Y_COUNT+1) is the number of single transfers in a 2D transfer). This field is an unsigned number in the range [0, 65535], representing 1 through 65536 iterations.

7.9.3.14 DMAC_CH_DESCR_Y_INCR

Description: Channel descriptor Y increment
Address: 0x402A1078
Offset: 0x78
Retention: Not Retained
IsDeepSleep: No
Comment: Copy of DESCR_Y_INCR of the currently active descriptor.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SRC_Y [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SRC_Y [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DST_Y [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DST_Y [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	SRC_Y	R	R	Undefined	Specifies increment of source address for each Y loop iteration (in multiples of SRC_TRANSFER_SIZE). This field is a signed number in the range [-32768, 32767].
16:31	DST_Y	R	R	Undefined	Specifies increment of destination address for each Y loop iteration (in multiples of DST_TRANSFER_SIZE). This field is a signed number in the range [-32768, 32767].

7.9.3.15 DMAC_CH_DESCR_NEXT

Description: Channel descriptor next pointer

Address: 0x402A107C

Offset: 0x7C

Retention: Not Retained

IsDeepSleep: No

Comment: Copy of DESCR_NEXT_PTR of the currently active descriptor. For a single transfer descriptor type, this register is at offset 0x0c. For a 1D transfer descriptor type, this register is at offset 0x14. For a 2D transfer descriptor type, this register is at offset 0x1c. For a memory copy transfer descriptor type, this register is at offset 0x10. For a scatter transfer descriptor type, this register is at offset 0x0c.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	PTR	R	R	Undefined	Address of next descriptor in descriptor list. When this field is '0', this is the last descriptor in the descriptor list.

7.9.3.16 DMAC_CH_INTR

Description: Interrupt
Address: 0x402A1080
Offset: 0x80
Retention: Not Retained
IsDeepSleep: No
Comment: The register fields are not retained. This is to ensure that they come up as '0' after coming out of DeepSleep system power mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DESCR_BUS_ERROR [7:7]	ACTIVE_CH_DISABLED [6:6]	CURR_PTR_NULL [5:5]	DST_MISAL [4:4]	SRC_MISAL [3:3]	DST_BUS_ERROR [2:2]	SRC_BUS_ERROR [1:1]	COMPLETION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	COMPLETION	RW1C	RW1C	0	Activated (set to '1') on completion of data transfer(s) as specified by the descriptor's CH_DESCR_CTL.INTR_TYPE.
1	SRC_BUS_ERROR	RW1C	RW1C	0	Activated (set to '1') on a bus error for a load from the source.
2	DST_BUS_ERROR	RW1C	RW1C	0	Activated (set to '1') on a bus error for a store to the destination.
3	SRC_MISAL	RW1C	RW1C	0	Activated (set to '1') on a misalignment of the source address.
4	DST_MISAL	RW1C	RW1C	0	Activated (set to '1') on a misalignment of the destination address.
5	CURR_PTR_NULL	RW1C	RW1C	0	Activated (set to '1') when the channel is enabled (CH_CTL.ENABLED is '1') and CH_CURR_PTR is '0'.
6	ACTIVE_CH_DISABLED	RW1C	RW1C	0	Activated (set to '1') if the channel is disabled by SW (accidentally/incorrectly) when the data transfer engine is busy.
7	DESCR_BUS_ERROR	RW1C	RW1C	0	Activated (set to '1') on a bus error for a load of the descriptor.

7.9.3.17 DMAC_CH_INTR_SET

Description: Interrupt set
Address: 0x402A1084
Offset: 0x84
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the INTR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DESCR_BUS_ERROR [7:7]	ACTIVE_CH_DISABLED [6:6]	CURR_PTR_NULL [5:5]	DST_MISAL [4:4]	SRC_MISAL [3:3]	DST_BUS_ERROR [2:2]	SRC_BUS_ERROR [1:1]	COMPLETION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	COMPLETION	RW1S	RW1S	0	Write this field with '1' to set INTR.COMPLETION field to '1' (a write of '0' has no effect).
1	SRC_BUS_ERROR	RW1S	RW1S	0	Write this field with '1' to set INTR.SRC_BUS_ERROR field to '1' (a write of '0' has no effect).
2	DST_BUS_ERROR	RW1S	RW1S	0	Write this field with '1' to set INTR.DST_BUS_ERROR field to '1' (a write of '0' has no effect).
3	SRC_MISAL	RW1S	RW1S	0	Write this field with '1' to set INTR.SRC_MISAL field to '1' (a write of '0' has no effect).
4	DST_MISAL	RW1S	RW1S	0	Write this field with '1' to set INTR.DST_MISAL field to '1' (a write of '0' has no effect).
5	CURR_PTR_NULL	RW1S	RW1S	0	Write this field with '1' to set INTR.CURR_PTR_NULL field to '1' (a write of '0' has no effect).
6	ACTIVE_CH_DISABLED	RW1S	RW1S	0	Write this field with '1' to set INTR.ACT_CH_DISABLED field to '1' (a write of '0' has no effect).
7	DESCR_BUS_ERROR	RW1S	RW1S	0	Write this field with '1' to set INTR.DESCR_BUS_ERROR field to '1' (a write of '0' has no effect).

7.9.3.18 DMAC_CH_INTR_MASK

Description: Interrupt mask
Address: 0x402A1088
Offset: 0x88
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DESCR_BUS_ERROR [7:7]	ACTIVE_CH_DISABLED [6:6]	CURR_PTR_NULL [5:5]	DST_MISAL [4:4]	SRC_MISAL [3:3]	DST_BUS_ERROR [2:2]	SRC_BUS_ERROR [1:1]	COMPLETION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	COMPLETION	RW	RW	0	Mask for INTR.COMPLETION interrupt.
1	SRC_BUS_ERROR	RW	RW	0	Mask for INTR.SRC_BUS_ERROR interrupt.
2	DST_BUS_ERROR	RW	RW	0	Mask for INTR.DST_BUS_ERROR interrupt.
3	SRC_MISAL	RW	RW	0	Mask for INTR.SRC_MISAL interrupt.
4	DST_MISAL	RW	RW	0	Mask for INTR.DST_MISAL interrupt.
5	CURR_PTR_NULL	RW	RW	0	Mask for INTR.CURR_PTR_NULL interrupt.
6	ACTIVE_CH_DISABLED	RW	RW	0	Mask for INTR.ACTIVE_CH_DISABLED interrupt.
7	DESCR_BUS_ERROR	RW	RW	0	Mask for INTR.DESCR_BUS_ERROR interrupt.

7.9.3.19 DMAC_CH_INTR_MASKED

Description: Interrupt masked
Address: 0x402A108C
Offset: 0x8C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise AND between the INTR and INTR_MASK registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for INTR and one for INTR_MASK. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_MASKED != 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DESCR_BUS_ERROR [7:7]	ACTIVE_CH_DISABLED [6:6]	CURR_PTR_NULL [5:5]	DST_MISAL [4:4]	SRC_MISAL [3:3]	DST_BUS_ERROR [2:2]	SRC_BUS_ERROR [1:1]	COMPLETION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	COMPLETION	R	R	0	Logical and of corresponding INTR.COMPLETION and INTR_MASK.COMPLETION fields.
1	SRC_BUS_ERROR	R	R	0	Logical and of corresponding INTR.SRC_BUS_ERROR and INTR_MASK.SRC_BUS_ERROR fields.
2	DST_BUS_ERROR	R	R	0	Logical and of corresponding INTR.DST_BUS_ERROR and INTR_MASK.DST_BUS_ERROR fields.
3	SRC_MISAL	R	R	0	Logical and of corresponding INTR.SRC_MISAL and INTR_MASK.SRC_MISAL fields.
4	DST_MISAL	R	R	0	Logical and of corresponding INTR.DST_MISAL and INTR_MASK.DST_MISAL fields.
5	CURR_PTR_NULL	R	R	0	Logical and of corresponding INTR.CURR_PTR_NULL and INTR_MASK.CURR_PTR_NULL fields.
6	ACTIVE_CH_DISABLED	R	R	0	Logical and of corresponding INTR.ACTIVE_CH_DISABLED and INTR_MASK.ACTIVE_CH_DISABLED fields.
7	DESCR_BUS_ERROR	R	R	0	Logical and of corresponding INTR.DESCR_BUS_ERROR and INTR_MASK.DESCR_BUS_ERROR fields.

8 DW

8.1 DW 0

Description	Datawire Controller
Base Address	0x40280000
Size	0x10000
Slave Num	MMIO2 - 7

8.1.1 0

Register Name	Address	Permission	Description
DW0_CTL0	0x40280000	FULL	Control
DW0_STATUS0	0x40280004	FULL	Status
DW0_ACT_DESCR_CTL0	0x40280020	FULL	Active descriptor control
DW0_ACT_DESCR_SRC0	0x40280024	FULL	Active descriptor source
DW0_ACT_DESCR_DST0	0x40280028	FULL	Active descriptor destination
DW0_ACT_DESCR_X_CTL0	0x40280030	FULL	Active descriptor X loop control
DW0_ACT_DESCR_Y_CTL0	0x40280034	FULL	Active descriptor Y loop control
DW0_ACT_DESCR_NEXT_PTR0	0x40280038	FULL	Active descriptor next pointer
DW0_ACT_SRC0	0x40280040	FULL	Active source
DW0_ACT_DST0	0x40280044	FULL	Active destination
DW0_ECC_CTL0	0x40280080	FULL	ECC control
DW0_CRC_CTL0	0x40280100	FULL	CRC control
DW0_CRC_DATA_CTL0	0x40280110	FULL	CRC data control
DW0_CRC_POL_CTL0	0x40280120	FULL	CRC polynomial control
DW0_CRC_LFSR_CTL0	0x40280130	FULL	CRC LFSR control
DW0_CRC_REM_CTL0	0x40280140	FULL	CRC remainder control
DW0_CRC_REM_RESULT0	0x40280148	FULL	CRC remainder result

8.1.1.1 CH_STRUCT 0

Register Name	Address	Permission	Description
DW0_CH_STRUCT0_CH_CTL	0x40288000	FULL	Channel control
DW0_CH_STRUCT0_CH_STATUS	0x40288004	FULL	Channel status
DW0_CH_STRUCT0_CH_IDX	0x40288008	FULL	Channel current indices
DW0_CH_STRUCT0_CH_CURR_PTR	0x4028800C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT0_INTR	0x40288010	FULL	Interrupt
DW0_CH_STRUCT0_INTR_SET	0x40288014	FULL	Interrupt set
DW0_CH_STRUCT0_INTR_MASK	0x40288018	FULL	Interrupt mask
DW0_CH_STRUCT0_INTR_MASKED	0x4028801C	FULL	Interrupt masked
DW0_CH_STRUCT0_SRAM_DATA0	0x40288020	FULL	SRAM data 0
DW0_CH_STRUCT0_SRAM_DATA1	0x40288024	FULL	SRAM data 1
DW0_CH_STRUCT0_TR_CMD	0x40288028	FULL	Channel software trigger

8.1.1.2 CH_STRUCT 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT1_CH_CTL	0x40288040	FULL	Channel control
DW0_CH_STRUCT1_CH_STATUS	0x40288044	FULL	Channel status
DW0_CH_STRUCT1_CH_IDX	0x40288048	FULL	Channel current indices
DW0_CH_STRUCT1_CH_CURR_PTR	0x4028804C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT1_INTR	0x40288050	FULL	Interrupt
DW0_CH_STRUCT1_INTR_SET	0x40288054	FULL	Interrupt set
DW0_CH_STRUCT1_INTR_MASK	0x40288058	FULL	Interrupt mask
DW0_CH_STRUCT1_INTR_MASKED	0x4028805C	FULL	Interrupt masked
DW0_CH_STRUCT1_SRAM_DATA0	0x40288060	FULL	SRAM data 0
DW0_CH_STRUCT1_SRAM_DATA1	0x40288064	FULL	SRAM data 1
DW0_CH_STRUCT1_TR_CMD	0x40288068	FULL	Channel software trigger

8.1.1.3 CH_STRUCT 2

Register Name	Address	Permission	Description
DW0_CH_STRUCT2_CH_CTL	0x40288080	FULL	Channel control
DW0_CH_STRUCT2_CH_STATUS	0x40288084	FULL	Channel status
DW0_CH_STRUCT2_CH_IDX	0x40288088	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT2_CH_CURR_PTR	0x4028808C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT2_INTR	0x40288090	FULL	Interrupt
DW0_CH_STRUCT2_INTR_SET	0x40288094	FULL	Interrupt set
DW0_CH_STRUCT2_INTR_MASK	0x40288098	FULL	Interrupt mask
DW0_CH_STRUCT2_INTR_MASKED	0x4028809C	FULL	Interrupt masked
DW0_CH_STRUCT2_SRAM_DATA0	0x402880A0	FULL	SRAM data 0
DW0_CH_STRUCT2_SRAM_DATA1	0x402880A4	FULL	SRAM data 1
DW0_CH_STRUCT2_TR_CMD	0x402880A8	FULL	Channel software trigger

8.1.1.4 CH_STRUCT 3

Register Name	Address	Permission	Description
DW0_CH_STRUCT3_CH_CTL	0x402880C0	FULL	Channel control
DW0_CH_STRUCT3_CH_STATUS	0x402880C4	FULL	Channel status
DW0_CH_STRUCT3_CH_IDX	0x402880C8	FULL	Channel current indices
DW0_CH_STRUCT3_CH_CURR_PTR	0x402880CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT3_INTR	0x402880D0	FULL	Interrupt
DW0_CH_STRUCT3_INTR_SET	0x402880D4	FULL	Interrupt set
DW0_CH_STRUCT3_INTR_MASK	0x402880D8	FULL	Interrupt mask
DW0_CH_STRUCT3_INTR_MASKED	0x402880DC	FULL	Interrupt masked
DW0_CH_STRUCT3_SRAM_DATA0	0x402880E0	FULL	SRAM data 0
DW0_CH_STRUCT3_SRAM_DATA1	0x402880E4	FULL	SRAM data 1
DW0_CH_STRUCT3_TR_CMD	0x402880E8	FULL	Channel software trigger

8.1.1.5 CH_STRUCT 4

Register Name	Address	Permission	Description
DW0_CH_STRUCT4_CH_CTL	0x40288100	FULL	Channel control
DW0_CH_STRUCT4_CH_STATUS	0x40288104	FULL	Channel status
DW0_CH_STRUCT4_CH_IDX	0x40288108	FULL	Channel current indices
DW0_CH_STRUCT4_CH_CURR_PTR	0x4028810C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT4_INTR	0x40288110	FULL	Interrupt
DW0_CH_STRUCT4_INTR_SET	0x40288114	FULL	Interrupt set
DW0_CH_STRUCT4_INTR_MASK	0x40288118	FULL	Interrupt mask
DW0_CH_STRUCT4_INTR_MASKED	0x4028811C	FULL	Interrupt masked
DW0_CH_STRUCT4_SRAM_DATA0	0x40288120	FULL	SRAM data 0
DW0_CH_STRUCT4_SRAM_DATA1	0x40288124	FULL	SRAM data 1
DW0_CH_STRUCT4_TR_CMD	0x40288128	FULL	Channel software trigger

8.1.1.6 CH_STRUCT 5

Register Name	Address	Permission	Description
DW0_CH_STRUCT5_CH_CTL	0x40288140	FULL	Channel control
DW0_CH_STRUCT5_CH_STATUS	0x40288144	FULL	Channel status
DW0_CH_STRUCT5_CH_IDX	0x40288148	FULL	Channel current indices
DW0_CH_STRUCT5_CH_CURR_PTR	0x4028814C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT5_INTR	0x40288150	FULL	Interrupt
DW0_CH_STRUCT5_INTR_SET	0x40288154	FULL	Interrupt set
DW0_CH_STRUCT5_INTR_MASK	0x40288158	FULL	Interrupt mask
DW0_CH_STRUCT5_INTR_MASKED	0x4028815C	FULL	Interrupt masked
DW0_CH_STRUCT5_SRAM_DATA0	0x40288160	FULL	SRAM data 0
DW0_CH_STRUCT5_SRAM_DATA1	0x40288164	FULL	SRAM data 1
DW0_CH_STRUCT5_TR_CMD	0x40288168	FULL	Channel software trigger

8.1.1.7 CH_STRUCT 6

Register Name	Address	Permission	Description
DW0_CH_STRUCT6_CH_CTL	0x40288180	FULL	Channel control
DW0_CH_STRUCT6_CH_STATUS	0x40288184	FULL	Channel status
DW0_CH_STRUCT6_CH_IDX	0x40288188	FULL	Channel current indices
DW0_CH_STRUCT6_CH_CURR_PTR	0x4028818C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT6_INTR	0x40288190	FULL	Interrupt
DW0_CH_STRUCT6_INTR_SET	0x40288194	FULL	Interrupt set
DW0_CH_STRUCT6_INTR_MASK	0x40288198	FULL	Interrupt mask
DW0_CH_STRUCT6_INTR_MASKED	0x4028819C	FULL	Interrupt masked
DW0_CH_STRUCT6_SRAM_DATA0	0x402881A0	FULL	SRAM data 0
DW0_CH_STRUCT6_SRAM_DATA1	0x402881A4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT6_TR_CMD	0x402881A8	FULL	Channel software trigger

8.1.1.8 CH_STRUCT 7

Register Name	Address	Permission	Description
DW0_CH_STRUCT7_CH_CTL	0x402881C0	FULL	Channel control
DW0_CH_STRUCT7_CH_STATUS	0x402881C4	FULL	Channel status
DW0_CH_STRUCT7_CH_IDX	0x402881C8	FULL	Channel current indices
DW0_CH_STRUCT7_CH_CURR_PTR	0x402881CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT7_INTR	0x402881D0	FULL	Interrupt
DW0_CH_STRUCT7_INTR_SET	0x402881D4	FULL	Interrupt set
DW0_CH_STRUCT7_INTR_MASK	0x402881D8	FULL	Interrupt mask
DW0_CH_STRUCT7_INTR_MASKED	0x402881DC	FULL	Interrupt masked
DW0_CH_STRUCT7_SRAM_DATA0	0x402881E0	FULL	SRAM data 0
DW0_CH_STRUCT7_SRAM_DATA1	0x402881E4	FULL	SRAM data 1
DW0_CH_STRUCT7_TR_CMD	0x402881E8	FULL	Channel software trigger

8.1.1.9 CH_STRUCT 8

Register Name	Address	Permission	Description
DW0_CH_STRUCT8_CH_CTL	0x40288200	FULL	Channel control
DW0_CH_STRUCT8_CH_STATUS	0x40288204	FULL	Channel status
DW0_CH_STRUCT8_CH_IDX	0x40288208	FULL	Channel current indices
DW0_CH_STRUCT8_CH_CURR_PTR	0x4028820C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT8_INTR	0x40288210	FULL	Interrupt
DW0_CH_STRUCT8_INTR_SET	0x40288214	FULL	Interrupt set
DW0_CH_STRUCT8_INTR_MASK	0x40288218	FULL	Interrupt mask
DW0_CH_STRUCT8_INTR_MASKED	0x4028821C	FULL	Interrupt masked
DW0_CH_STRUCT8_SRAM_DATA0	0x40288220	FULL	SRAM data 0
DW0_CH_STRUCT8_SRAM_DATA1	0x40288224	FULL	SRAM data 1
DW0_CH_STRUCT8_TR_CMD	0x40288228	FULL	Channel software trigger

8.1.1.10 CH_STRUCT 9

Register Name	Address	Permission	Description
DW0_CH_STRUCT9_CH_CTL	0x40288240	FULL	Channel control
DW0_CH_STRUCT9_CH_STATUS	0x40288244	FULL	Channel status
DW0_CH_STRUCT9_CH_IDX	0x40288248	FULL	Channel current indices
DW0_CH_STRUCT9_CH_CURR_PTR	0x4028824C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT9_INTR	0x40288250	FULL	Interrupt
DW0_CH_STRUCT9_INTR_SET	0x40288254	FULL	Interrupt set
DW0_CH_STRUCT9_INTR_MASK	0x40288258	FULL	Interrupt mask
DW0_CH_STRUCT9_INTR_MASKED	0x4028825C	FULL	Interrupt masked
DW0_CH_STRUCT9_SRAM_DATA0	0x40288260	FULL	SRAM data 0
DW0_CH_STRUCT9_SRAM_DATA1	0x40288264	FULL	SRAM data 1
DW0_CH_STRUCT9_TR_CMD	0x40288268	FULL	Channel software trigger

8.1.1.11 CH_STRUCT 10

Register Name	Address	Permission	Description
DW0_CH_STRUCT10_CH_CTL	0x40288280	FULL	Channel control
DW0_CH_STRUCT10_CH_STATUS	0x40288284	FULL	Channel status
DW0_CH_STRUCT10_CH_IDX	0x40288288	FULL	Channel current indices
DW0_CH_STRUCT10_CH_CURR_PTR	0x4028828C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT10_INTR	0x40288290	FULL	Interrupt
DW0_CH_STRUCT10_INTR_SET	0x40288294	FULL	Interrupt set
DW0_CH_STRUCT10_INTR_MASK	0x40288298	FULL	Interrupt mask
DW0_CH_STRUCT10_INTR_MASKED	0x4028829C	FULL	Interrupt masked
DW0_CH_STRUCT10_SRAM_DATA0	0x402882A0	FULL	SRAM data 0
DW0_CH_STRUCT10_SRAM_DATA1	0x402882A4	FULL	SRAM data 1
DW0_CH_STRUCT10_TR_CMD	0x402882A8	FULL	Channel software trigger

8.1.1.12 CH_STRUCT 11

Register Name	Address	Permission	Description
DW0_CH_STRUCT11_CH_CTL	0x402882C0	FULL	Channel control
DW0_CH_STRUCT11_CH_STATUS	0x402882C4	FULL	Channel status
DW0_CH_STRUCT11_CH_IDX	0x402882C8	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT11_CH_CURR_PTR	0x402882CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT11_INTR	0x402882D0	FULL	Interrupt
DW0_CH_STRUCT11_INTR_SET	0x402882D4	FULL	Interrupt set
DW0_CH_STRUCT11_INTR_MASK	0x402882D8	FULL	Interrupt mask
DW0_CH_STRUCT11_INTR_MASKED	0x402882DC	FULL	Interrupt masked
DW0_CH_STRUCT11_SRAM_DATA0	0x402882E0	FULL	SRAM data 0
DW0_CH_STRUCT11_SRAM_DATA1	0x402882E4	FULL	SRAM data 1
DW0_CH_STRUCT11_TR_CMD	0x402882E8	FULL	Channel software trigger

8.1.1.13 CH_STRUCT 12

Register Name	Address	Permission	Description
DW0_CH_STRUCT12_CH_CTL	0x40288300	FULL	Channel control
DW0_CH_STRUCT12_CH_STATUS	0x40288304	FULL	Channel status
DW0_CH_STRUCT12_CH_IDX	0x40288308	FULL	Channel current indices
DW0_CH_STRUCT12_CH_CURR_PTR	0x4028830C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT12_INTR	0x40288310	FULL	Interrupt
DW0_CH_STRUCT12_INTR_SET	0x40288314	FULL	Interrupt set
DW0_CH_STRUCT12_INTR_MASK	0x40288318	FULL	Interrupt mask
DW0_CH_STRUCT12_INTR_MASKED	0x4028831C	FULL	Interrupt masked
DW0_CH_STRUCT12_SRAM_DATA0	0x40288320	FULL	SRAM data 0
DW0_CH_STRUCT12_SRAM_DATA1	0x40288324	FULL	SRAM data 1
DW0_CH_STRUCT12_TR_CMD	0x40288328	FULL	Channel software trigger

8.1.1.14 CH_STRUCT 13

Register Name	Address	Permission	Description
DW0_CH_STRUCT13_CH_CTL	0x40288340	FULL	Channel control
DW0_CH_STRUCT13_CH_STATUS	0x40288344	FULL	Channel status
DW0_CH_STRUCT13_CH_IDX	0x40288348	FULL	Channel current indices
DW0_CH_STRUCT13_CH_CURR_PTR	0x4028834C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT13_INTR	0x40288350	FULL	Interrupt
DW0_CH_STRUCT13_INTR_SET	0x40288354	FULL	Interrupt set
DW0_CH_STRUCT13_INTR_MASK	0x40288358	FULL	Interrupt mask
DW0_CH_STRUCT13_INTR_MASKED	0x4028835C	FULL	Interrupt masked
DW0_CH_STRUCT13_SRAM_DATA0	0x40288360	FULL	SRAM data 0
DW0_CH_STRUCT13_SRAM_DATA1	0x40288364	FULL	SRAM data 1
DW0_CH_STRUCT13_TR_CMD	0x40288368	FULL	Channel software trigger

8.1.1.15 CH_STRUCT 14

Register Name	Address	Permission	Description
DW0_CH_STRUCT14_CH_CTL	0x40288380	FULL	Channel control
DW0_CH_STRUCT14_CH_STATUS	0x40288384	FULL	Channel status
DW0_CH_STRUCT14_CH_IDX	0x40288388	FULL	Channel current indices
DW0_CH_STRUCT14_CH_CURR_PTR	0x4028838C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT14_INTR	0x40288390	FULL	Interrupt
DW0_CH_STRUCT14_INTR_SET	0x40288394	FULL	Interrupt set
DW0_CH_STRUCT14_INTR_MASK	0x40288398	FULL	Interrupt mask
DW0_CH_STRUCT14_INTR_MASKED	0x4028839C	FULL	Interrupt masked
DW0_CH_STRUCT14_SRAM_DATA0	0x402883A0	FULL	SRAM data 0
DW0_CH_STRUCT14_SRAM_DATA1	0x402883A4	FULL	SRAM data 1
DW0_CH_STRUCT14_TR_CMD	0x402883A8	FULL	Channel software trigger

8.1.1.16 CH_STRUCT 15

Register Name	Address	Permission	Description
DW0_CH_STRUCT15_CH_CTL	0x402883C0	FULL	Channel control
DW0_CH_STRUCT15_CH_STATUS	0x402883C4	FULL	Channel status
DW0_CH_STRUCT15_CH_IDX	0x402883C8	FULL	Channel current indices
DW0_CH_STRUCT15_CH_CURR_PTR	0x402883CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT15_INTR	0x402883D0	FULL	Interrupt
DW0_CH_STRUCT15_INTR_SET	0x402883D4	FULL	Interrupt set
DW0_CH_STRUCT15_INTR_MASK	0x402883D8	FULL	Interrupt mask
DW0_CH_STRUCT15_INTR_MASKED	0x402883DC	FULL	Interrupt masked
DW0_CH_STRUCT15_SRAM_DATA0	0x402883E0	FULL	SRAM data 0
DW0_CH_STRUCT15_SRAM_DATA1	0x402883E4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT15_TR_CMD	0x402883E8	FULL	Channel software trigger

8.1.1.17 CH_STRUCT 16

Register Name	Address	Permission	Description
DW0_CH_STRUCT16_CH_CTL	0x40288400	FULL	Channel control
DW0_CH_STRUCT16_CH_STATUS	0x40288404	FULL	Channel status
DW0_CH_STRUCT16_CH_IDX	0x40288408	FULL	Channel current indices
DW0_CH_STRUCT16_CH_CURR_PTR	0x4028840C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT16_INTR	0x40288410	FULL	Interrupt
DW0_CH_STRUCT16_INTR_SET	0x40288414	FULL	Interrupt set
DW0_CH_STRUCT16_INTR_MASK	0x40288418	FULL	Interrupt mask
DW0_CH_STRUCT16_INTR_MASKED	0x4028841C	FULL	Interrupt masked
DW0_CH_STRUCT16_SRAM_DATA0	0x40288420	FULL	SRAM data 0
DW0_CH_STRUCT16_SRAM_DATA1	0x40288424	FULL	SRAM data 1
DW0_CH_STRUCT16_TR_CMD	0x40288428	FULL	Channel software trigger

8.1.1.18 CH_STRUCT 17

Register Name	Address	Permission	Description
DW0_CH_STRUCT17_CH_CTL	0x40288440	FULL	Channel control
DW0_CH_STRUCT17_CH_STATUS	0x40288444	FULL	Channel status
DW0_CH_STRUCT17_CH_IDX	0x40288448	FULL	Channel current indices
DW0_CH_STRUCT17_CH_CURR_PTR	0x4028844C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT17_INTR	0x40288450	FULL	Interrupt
DW0_CH_STRUCT17_INTR_SET	0x40288454	FULL	Interrupt set
DW0_CH_STRUCT17_INTR_MASK	0x40288458	FULL	Interrupt mask
DW0_CH_STRUCT17_INTR_MASKED	0x4028845C	FULL	Interrupt masked
DW0_CH_STRUCT17_SRAM_DATA0	0x40288460	FULL	SRAM data 0
DW0_CH_STRUCT17_SRAM_DATA1	0x40288464	FULL	SRAM data 1
DW0_CH_STRUCT17_TR_CMD	0x40288468	FULL	Channel software trigger

8.1.1.19 CH_STRUCT 18

Register Name	Address	Permission	Description
DW0_CH_STRUCT18_CH_CTL	0x40288480	FULL	Channel control
DW0_CH_STRUCT18_CH_STATUS	0x40288484	FULL	Channel status
DW0_CH_STRUCT18_CH_IDX	0x40288488	FULL	Channel current indices
DW0_CH_STRUCT18_CH_CURR_PTR	0x4028848C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT18_INTR	0x40288490	FULL	Interrupt
DW0_CH_STRUCT18_INTR_SET	0x40288494	FULL	Interrupt set
DW0_CH_STRUCT18_INTR_MASK	0x40288498	FULL	Interrupt mask
DW0_CH_STRUCT18_INTR_MASKED	0x4028849C	FULL	Interrupt masked
DW0_CH_STRUCT18_SRAM_DATA0	0x402884A0	FULL	SRAM data 0
DW0_CH_STRUCT18_SRAM_DATA1	0x402884A4	FULL	SRAM data 1
DW0_CH_STRUCT18_TR_CMD	0x402884A8	FULL	Channel software trigger

8.1.1.20 CH_STRUCT 19

Register Name	Address	Permission	Description
DW0_CH_STRUCT19_CH_CTL	0x402884C0	FULL	Channel control
DW0_CH_STRUCT19_CH_STATUS	0x402884C4	FULL	Channel status
DW0_CH_STRUCT19_CH_IDX	0x402884C8	FULL	Channel current indices
DW0_CH_STRUCT19_CH_CURR_PTR	0x402884CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT19_INTR	0x402884D0	FULL	Interrupt
DW0_CH_STRUCT19_INTR_SET	0x402884D4	FULL	Interrupt set
DW0_CH_STRUCT19_INTR_MASK	0x402884D8	FULL	Interrupt mask
DW0_CH_STRUCT19_INTR_MASKED	0x402884DC	FULL	Interrupt masked
DW0_CH_STRUCT19_SRAM_DATA0	0x402884E0	FULL	SRAM data 0
DW0_CH_STRUCT19_SRAM_DATA1	0x402884E4	FULL	SRAM data 1
DW0_CH_STRUCT19_TR_CMD	0x402884E8	FULL	Channel software trigger

8.1.1.21 CH_STRUCT 20

Register Name	Address	Permission	Description
DW0_CH_STRUCT20_CH_CTL	0x40288500	FULL	Channel control
DW0_CH_STRUCT20_CH_STATUS	0x40288504	FULL	Channel status
DW0_CH_STRUCT20_CH_IDX	0x40288508	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT20_CH_CURR_PTR	0x4028850C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT20_INTR	0x40288510	FULL	Interrupt
DW0_CH_STRUCT20_INTR_SET	0x40288514	FULL	Interrupt set
DW0_CH_STRUCT20_INTR_MASK	0x40288518	FULL	Interrupt mask
DW0_CH_STRUCT20_INTR_MASKED	0x4028851C	FULL	Interrupt masked
DW0_CH_STRUCT20_SRAM_DATA0	0x40288520	FULL	SRAM data 0
DW0_CH_STRUCT20_SRAM_DATA1	0x40288524	FULL	SRAM data 1
DW0_CH_STRUCT20_TR_CMD	0x40288528	FULL	Channel software trigger

8.1.1.22 CH_STRUCT 21

Register Name	Address	Permission	Description
DW0_CH_STRUCT21_CH_CTL	0x40288540	FULL	Channel control
DW0_CH_STRUCT21_CH_STATUS	0x40288544	FULL	Channel status
DW0_CH_STRUCT21_CH_IDX	0x40288548	FULL	Channel current indices
DW0_CH_STRUCT21_CH_CURR_PTR	0x4028854C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT21_INTR	0x40288550	FULL	Interrupt
DW0_CH_STRUCT21_INTR_SET	0x40288554	FULL	Interrupt set
DW0_CH_STRUCT21_INTR_MASK	0x40288558	FULL	Interrupt mask
DW0_CH_STRUCT21_INTR_MASKED	0x4028855C	FULL	Interrupt masked
DW0_CH_STRUCT21_SRAM_DATA0	0x40288560	FULL	SRAM data 0
DW0_CH_STRUCT21_SRAM_DATA1	0x40288564	FULL	SRAM data 1
DW0_CH_STRUCT21_TR_CMD	0x40288568	FULL	Channel software trigger

8.1.1.23 CH_STRUCT 22

Register Name	Address	Permission	Description
DW0_CH_STRUCT22_CH_CTL	0x40288580	FULL	Channel control
DW0_CH_STRUCT22_CH_STATUS	0x40288584	FULL	Channel status
DW0_CH_STRUCT22_CH_IDX	0x40288588	FULL	Channel current indices
DW0_CH_STRUCT22_CH_CURR_PTR	0x4028858C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT22_INTR	0x40288590	FULL	Interrupt
DW0_CH_STRUCT22_INTR_SET	0x40288594	FULL	Interrupt set
DW0_CH_STRUCT22_INTR_MASK	0x40288598	FULL	Interrupt mask
DW0_CH_STRUCT22_INTR_MASKED	0x4028859C	FULL	Interrupt masked
DW0_CH_STRUCT22_SRAM_DATA0	0x402885A0	FULL	SRAM data 0
DW0_CH_STRUCT22_SRAM_DATA1	0x402885A4	FULL	SRAM data 1
DW0_CH_STRUCT22_TR_CMD	0x402885A8	FULL	Channel software trigger

8.1.1.24 CH_STRUCT 23

Register Name	Address	Permission	Description
DW0_CH_STRUCT23_CH_CTL	0x402885C0	FULL	Channel control
DW0_CH_STRUCT23_CH_STATUS	0x402885C4	FULL	Channel status
DW0_CH_STRUCT23_CH_IDX	0x402885C8	FULL	Channel current indices
DW0_CH_STRUCT23_CH_CURR_PTR	0x402885CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT23_INTR	0x402885D0	FULL	Interrupt
DW0_CH_STRUCT23_INTR_SET	0x402885D4	FULL	Interrupt set
DW0_CH_STRUCT23_INTR_MASK	0x402885D8	FULL	Interrupt mask
DW0_CH_STRUCT23_INTR_MASKED	0x402885DC	FULL	Interrupt masked
DW0_CH_STRUCT23_SRAM_DATA0	0x402885E0	FULL	SRAM data 0
DW0_CH_STRUCT23_SRAM_DATA1	0x402885E4	FULL	SRAM data 1
DW0_CH_STRUCT23_TR_CMD	0x402885E8	FULL	Channel software trigger

8.1.1.25 CH_STRUCT 24

Register Name	Address	Permission	Description
DW0_CH_STRUCT24_CH_CTL	0x40288600	FULL	Channel control
DW0_CH_STRUCT24_CH_STATUS	0x40288604	FULL	Channel status
DW0_CH_STRUCT24_CH_IDX	0x40288608	FULL	Channel current indices
DW0_CH_STRUCT24_CH_CURR_PTR	0x4028860C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT24_INTR	0x40288610	FULL	Interrupt
DW0_CH_STRUCT24_INTR_SET	0x40288614	FULL	Interrupt set
DW0_CH_STRUCT24_INTR_MASK	0x40288618	FULL	Interrupt mask
DW0_CH_STRUCT24_INTR_MASKED	0x4028861C	FULL	Interrupt masked
DW0_CH_STRUCT24_SRAM_DATA0	0x40288620	FULL	SRAM data 0
DW0_CH_STRUCT24_SRAM_DATA1	0x40288624	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT24_TR_CMD	0x40288628	FULL	Channel software trigger

8.1.1.26 CH_STRUCT 25

Register Name	Address	Permission	Description
DW0_CH_STRUCT25_CH_CTL	0x40288640	FULL	Channel control
DW0_CH_STRUCT25_CH_STATUS	0x40288644	FULL	Channel status
DW0_CH_STRUCT25_CH_IDX	0x40288648	FULL	Channel current indices
DW0_CH_STRUCT25_CH_CURR_PTR	0x4028864C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT25_INTR	0x40288650	FULL	Interrupt
DW0_CH_STRUCT25_INTR_SET	0x40288654	FULL	Interrupt set
DW0_CH_STRUCT25_INTR_MASK	0x40288658	FULL	Interrupt mask
DW0_CH_STRUCT25_INTR_MASKED	0x4028865C	FULL	Interrupt masked
DW0_CH_STRUCT25_SRAM_DATA0	0x40288660	FULL	SRAM data 0
DW0_CH_STRUCT25_SRAM_DATA1	0x40288664	FULL	SRAM data 1
DW0_CH_STRUCT25_TR_CMD	0x40288668	FULL	Channel software trigger

8.1.1.27 CH_STRUCT 26

Register Name	Address	Permission	Description
DW0_CH_STRUCT26_CH_CTL	0x40288680	FULL	Channel control
DW0_CH_STRUCT26_CH_STATUS	0x40288684	FULL	Channel status
DW0_CH_STRUCT26_CH_IDX	0x40288688	FULL	Channel current indices
DW0_CH_STRUCT26_CH_CURR_PTR	0x4028868C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT26_INTR	0x40288690	FULL	Interrupt
DW0_CH_STRUCT26_INTR_SET	0x40288694	FULL	Interrupt set
DW0_CH_STRUCT26_INTR_MASK	0x40288698	FULL	Interrupt mask
DW0_CH_STRUCT26_INTR_MASKED	0x4028869C	FULL	Interrupt masked
DW0_CH_STRUCT26_SRAM_DATA0	0x402886A0	FULL	SRAM data 0
DW0_CH_STRUCT26_SRAM_DATA1	0x402886A4	FULL	SRAM data 1
DW0_CH_STRUCT26_TR_CMD	0x402886A8	FULL	Channel software trigger

8.1.1.28 CH_STRUCT 27

Register Name	Address	Permission	Description
DW0_CH_STRUCT27_CH_CTL	0x402886C0	FULL	Channel control
DW0_CH_STRUCT27_CH_STATUS	0x402886C4	FULL	Channel status
DW0_CH_STRUCT27_CH_IDX	0x402886C8	FULL	Channel current indices
DW0_CH_STRUCT27_CH_CURR_PTR	0x402886CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT27_INTR	0x402886D0	FULL	Interrupt
DW0_CH_STRUCT27_INTR_SET	0x402886D4	FULL	Interrupt set
DW0_CH_STRUCT27_INTR_MASK	0x402886D8	FULL	Interrupt mask
DW0_CH_STRUCT27_INTR_MASKED	0x402886DC	FULL	Interrupt masked
DW0_CH_STRUCT27_SRAM_DATA0	0x402886E0	FULL	SRAM data 0
DW0_CH_STRUCT27_SRAM_DATA1	0x402886E4	FULL	SRAM data 1
DW0_CH_STRUCT27_TR_CMD	0x402886E8	FULL	Channel software trigger

8.1.1.29 CH_STRUCT 28

Register Name	Address	Permission	Description
DW0_CH_STRUCT28_CH_CTL	0x40288700	FULL	Channel control
DW0_CH_STRUCT28_CH_STATUS	0x40288704	FULL	Channel status
DW0_CH_STRUCT28_CH_IDX	0x40288708	FULL	Channel current indices
DW0_CH_STRUCT28_CH_CURR_PTR	0x4028870C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT28_INTR	0x40288710	FULL	Interrupt
DW0_CH_STRUCT28_INTR_SET	0x40288714	FULL	Interrupt set
DW0_CH_STRUCT28_INTR_MASK	0x40288718	FULL	Interrupt mask
DW0_CH_STRUCT28_INTR_MASKED	0x4028871C	FULL	Interrupt masked
DW0_CH_STRUCT28_SRAM_DATA0	0x40288720	FULL	SRAM data 0
DW0_CH_STRUCT28_SRAM_DATA1	0x40288724	FULL	SRAM data 1
DW0_CH_STRUCT28_TR_CMD	0x40288728	FULL	Channel software trigger

8.1.1.30 CH_STRUCT 29

Register Name	Address	Permission	Description
DW0_CH_STRUCT29_CH_CTL	0x40288740	FULL	Channel control
DW0_CH_STRUCT29_CH_STATUS	0x40288744	FULL	Channel status
DW0_CH_STRUCT29_CH_IDX	0x40288748	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT29_CH_CURR_PTR	0x4028874C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT29_INTR	0x40288750	FULL	Interrupt
DW0_CH_STRUCT29_INTR_SET	0x40288754	FULL	Interrupt set
DW0_CH_STRUCT29_INTR_MASK	0x40288758	FULL	Interrupt mask
DW0_CH_STRUCT29_INTR_MASKED	0x4028875C	FULL	Interrupt masked
DW0_CH_STRUCT29_SRAM_DATA0	0x40288760	FULL	SRAM data 0
DW0_CH_STRUCT29_SRAM_DATA1	0x40288764	FULL	SRAM data 1
DW0_CH_STRUCT29_TR_CMD	0x40288768	FULL	Channel software trigger

8.1.1.31 CH_STRUCT 30

Register Name	Address	Permission	Description
DW0_CH_STRUCT30_CH_CTL	0x40288780	FULL	Channel control
DW0_CH_STRUCT30_CH_STATUS	0x40288784	FULL	Channel status
DW0_CH_STRUCT30_CH_IDX	0x40288788	FULL	Channel current indices
DW0_CH_STRUCT30_CH_CURR_PTR	0x4028878C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT30_INTR	0x40288790	FULL	Interrupt
DW0_CH_STRUCT30_INTR_SET	0x40288794	FULL	Interrupt set
DW0_CH_STRUCT30_INTR_MASK	0x40288798	FULL	Interrupt mask
DW0_CH_STRUCT30_INTR_MASKED	0x4028879C	FULL	Interrupt masked
DW0_CH_STRUCT30_SRAM_DATA0	0x402887A0	FULL	SRAM data 0
DW0_CH_STRUCT30_SRAM_DATA1	0x402887A4	FULL	SRAM data 1
DW0_CH_STRUCT30_TR_CMD	0x402887A8	FULL	Channel software trigger

8.1.1.32 CH_STRUCT 31

Register Name	Address	Permission	Description
DW0_CH_STRUCT31_CH_CTL	0x402887C0	FULL	Channel control
DW0_CH_STRUCT31_CH_STATUS	0x402887C4	FULL	Channel status
DW0_CH_STRUCT31_CH_IDX	0x402887C8	FULL	Channel current indices
DW0_CH_STRUCT31_CH_CURR_PTR	0x402887CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT31_INTR	0x402887D0	FULL	Interrupt
DW0_CH_STRUCT31_INTR_SET	0x402887D4	FULL	Interrupt set
DW0_CH_STRUCT31_INTR_MASK	0x402887D8	FULL	Interrupt mask
DW0_CH_STRUCT31_INTR_MASKED	0x402887DC	FULL	Interrupt masked
DW0_CH_STRUCT31_SRAM_DATA0	0x402887E0	FULL	SRAM data 0
DW0_CH_STRUCT31_SRAM_DATA1	0x402887E4	FULL	SRAM data 1
DW0_CH_STRUCT31_TR_CMD	0x402887E8	FULL	Channel software trigger

8.1.1.33 CH_STRUCT 32

Register Name	Address	Permission	Description
DW0_CH_STRUCT32_CH_CTL	0x40288800	FULL	Channel control
DW0_CH_STRUCT32_CH_STATUS	0x40288804	FULL	Channel status
DW0_CH_STRUCT32_CH_IDX	0x40288808	FULL	Channel current indices
DW0_CH_STRUCT32_CH_CURR_PTR	0x4028880C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT32_INTR	0x40288810	FULL	Interrupt
DW0_CH_STRUCT32_INTR_SET	0x40288814	FULL	Interrupt set
DW0_CH_STRUCT32_INTR_MASK	0x40288818	FULL	Interrupt mask
DW0_CH_STRUCT32_INTR_MASKED	0x4028881C	FULL	Interrupt masked
DW0_CH_STRUCT32_SRAM_DATA0	0x40288820	FULL	SRAM data 0
DW0_CH_STRUCT32_SRAM_DATA1	0x40288824	FULL	SRAM data 1
DW0_CH_STRUCT32_TR_CMD	0x40288828	FULL	Channel software trigger

8.1.1.34 CH_STRUCT 33

Register Name	Address	Permission	Description
DW0_CH_STRUCT33_CH_CTL	0x40288840	FULL	Channel control
DW0_CH_STRUCT33_CH_STATUS	0x40288844	FULL	Channel status
DW0_CH_STRUCT33_CH_IDX	0x40288848	FULL	Channel current indices
DW0_CH_STRUCT33_CH_CURR_PTR	0x4028884C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT33_INTR	0x40288850	FULL	Interrupt
DW0_CH_STRUCT33_INTR_SET	0x40288854	FULL	Interrupt set
DW0_CH_STRUCT33_INTR_MASK	0x40288858	FULL	Interrupt mask
DW0_CH_STRUCT33_INTR_MASKED	0x4028885C	FULL	Interrupt masked
DW0_CH_STRUCT33_SRAM_DATA0	0x40288860	FULL	SRAM data 0
DW0_CH_STRUCT33_SRAM_DATA1	0x40288864	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT33_TR_CMD	0x40288868	FULL	Channel software trigger

8.1.1.35 CH_STRUCT 34

Register Name	Address	Permission	Description
DW0_CH_STRUCT34_CH_CTL	0x40288880	FULL	Channel control
DW0_CH_STRUCT34_CH_STATUS	0x40288884	FULL	Channel status
DW0_CH_STRUCT34_CH_IDX	0x40288888	FULL	Channel current indices
DW0_CH_STRUCT34_CH_CURR_PTR	0x4028888C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT34_INTR	0x40288890	FULL	Interrupt
DW0_CH_STRUCT34_INTR_SET	0x40288894	FULL	Interrupt set
DW0_CH_STRUCT34_INTR_MASK	0x40288898	FULL	Interrupt mask
DW0_CH_STRUCT34_INTR_MASKED	0x4028889C	FULL	Interrupt masked
DW0_CH_STRUCT34_SRAM_DATA0	0x402888A0	FULL	SRAM data 0
DW0_CH_STRUCT34_SRAM_DATA1	0x402888A4	FULL	SRAM data 1
DW0_CH_STRUCT34_TR_CMD	0x402888A8	FULL	Channel software trigger

8.1.1.36 CH_STRUCT 35

Register Name	Address	Permission	Description
DW0_CH_STRUCT35_CH_CTL	0x402888C0	FULL	Channel control
DW0_CH_STRUCT35_CH_STATUS	0x402888C4	FULL	Channel status
DW0_CH_STRUCT35_CH_IDX	0x402888C8	FULL	Channel current indices
DW0_CH_STRUCT35_CH_CURR_PTR	0x402888CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT35_INTR	0x402888D0	FULL	Interrupt
DW0_CH_STRUCT35_INTR_SET	0x402888D4	FULL	Interrupt set
DW0_CH_STRUCT35_INTR_MASK	0x402888D8	FULL	Interrupt mask
DW0_CH_STRUCT35_INTR_MASKED	0x402888DC	FULL	Interrupt masked
DW0_CH_STRUCT35_SRAM_DATA0	0x402888E0	FULL	SRAM data 0
DW0_CH_STRUCT35_SRAM_DATA1	0x402888E4	FULL	SRAM data 1
DW0_CH_STRUCT35_TR_CMD	0x402888E8	FULL	Channel software trigger

8.1.1.37 CH_STRUCT 36

Register Name	Address	Permission	Description
DW0_CH_STRUCT36_CH_CTL	0x40288900	FULL	Channel control
DW0_CH_STRUCT36_CH_STATUS	0x40288904	FULL	Channel status
DW0_CH_STRUCT36_CH_IDX	0x40288908	FULL	Channel current indices
DW0_CH_STRUCT36_CH_CURR_PTR	0x4028890C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT36_INTR	0x40288910	FULL	Interrupt
DW0_CH_STRUCT36_INTR_SET	0x40288914	FULL	Interrupt set
DW0_CH_STRUCT36_INTR_MASK	0x40288918	FULL	Interrupt mask
DW0_CH_STRUCT36_INTR_MASKED	0x4028891C	FULL	Interrupt masked
DW0_CH_STRUCT36_SRAM_DATA0	0x40288920	FULL	SRAM data 0
DW0_CH_STRUCT36_SRAM_DATA1	0x40288924	FULL	SRAM data 1
DW0_CH_STRUCT36_TR_CMD	0x40288928	FULL	Channel software trigger

8.1.1.38 CH_STRUCT 37

Register Name	Address	Permission	Description
DW0_CH_STRUCT37_CH_CTL	0x40288940	FULL	Channel control
DW0_CH_STRUCT37_CH_STATUS	0x40288944	FULL	Channel status
DW0_CH_STRUCT37_CH_IDX	0x40288948	FULL	Channel current indices
DW0_CH_STRUCT37_CH_CURR_PTR	0x4028894C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT37_INTR	0x40288950	FULL	Interrupt
DW0_CH_STRUCT37_INTR_SET	0x40288954	FULL	Interrupt set
DW0_CH_STRUCT37_INTR_MASK	0x40288958	FULL	Interrupt mask
DW0_CH_STRUCT37_INTR_MASKED	0x4028895C	FULL	Interrupt masked
DW0_CH_STRUCT37_SRAM_DATA0	0x40288960	FULL	SRAM data 0
DW0_CH_STRUCT37_SRAM_DATA1	0x40288964	FULL	SRAM data 1
DW0_CH_STRUCT37_TR_CMD	0x40288968	FULL	Channel software trigger

8.1.1.39 CH_STRUCT 38

Register Name	Address	Permission	Description
DW0_CH_STRUCT38_CH_CTL	0x40288980	FULL	Channel control
DW0_CH_STRUCT38_CH_STATUS	0x40288984	FULL	Channel status
DW0_CH_STRUCT38_CH_IDX	0x40288988	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT38_CH_CURR_PTR	0x4028898C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT38_INTR	0x40288990	FULL	Interrupt
DW0_CH_STRUCT38_INTR_SET	0x40288994	FULL	Interrupt set
DW0_CH_STRUCT38_INTR_MASK	0x40288998	FULL	Interrupt mask
DW0_CH_STRUCT38_INTR_MASKED	0x4028899C	FULL	Interrupt masked
DW0_CH_STRUCT38_SRAM_DATA0	0x402889A0	FULL	SRAM data 0
DW0_CH_STRUCT38_SRAM_DATA1	0x402889A4	FULL	SRAM data 1
DW0_CH_STRUCT38_TR_CMD	0x402889A8	FULL	Channel software trigger

8.1.1.40 CH_STRUCT 39

Register Name	Address	Permission	Description
DW0_CH_STRUCT39_CH_CTL	0x402889C0	FULL	Channel control
DW0_CH_STRUCT39_CH_STATUS	0x402889C4	FULL	Channel status
DW0_CH_STRUCT39_CH_IDX	0x402889C8	FULL	Channel current indices
DW0_CH_STRUCT39_CH_CURR_PTR	0x402889CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT39_INTR	0x402889D0	FULL	Interrupt
DW0_CH_STRUCT39_INTR_SET	0x402889D4	FULL	Interrupt set
DW0_CH_STRUCT39_INTR_MASK	0x402889D8	FULL	Interrupt mask
DW0_CH_STRUCT39_INTR_MASKED	0x402889DC	FULL	Interrupt masked
DW0_CH_STRUCT39_SRAM_DATA0	0x402889E0	FULL	SRAM data 0
DW0_CH_STRUCT39_SRAM_DATA1	0x402889E4	FULL	SRAM data 1
DW0_CH_STRUCT39_TR_CMD	0x402889E8	FULL	Channel software trigger

8.1.1.41 CH_STRUCT 40

Register Name	Address	Permission	Description
DW0_CH_STRUCT40_CH_CTL	0x40288A00	FULL	Channel control
DW0_CH_STRUCT40_CH_STATUS	0x40288A04	FULL	Channel status
DW0_CH_STRUCT40_CH_IDX	0x40288A08	FULL	Channel current indices
DW0_CH_STRUCT40_CH_CURR_PTR	0x40288A0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT40_INTR	0x40288A10	FULL	Interrupt
DW0_CH_STRUCT40_INTR_SET	0x40288A14	FULL	Interrupt set
DW0_CH_STRUCT40_INTR_MASK	0x40288A18	FULL	Interrupt mask
DW0_CH_STRUCT40_INTR_MASKED	0x40288A1C	FULL	Interrupt masked
DW0_CH_STRUCT40_SRAM_DATA0	0x40288A20	FULL	SRAM data 0
DW0_CH_STRUCT40_SRAM_DATA1	0x40288A24	FULL	SRAM data 1
DW0_CH_STRUCT40_TR_CMD	0x40288A28	FULL	Channel software trigger

8.1.1.42 CH_STRUCT 41

Register Name	Address	Permission	Description
DW0_CH_STRUCT41_CH_CTL	0x40288A40	FULL	Channel control
DW0_CH_STRUCT41_CH_STATUS	0x40288A44	FULL	Channel status
DW0_CH_STRUCT41_CH_IDX	0x40288A48	FULL	Channel current indices
DW0_CH_STRUCT41_CH_CURR_PTR	0x40288A4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT41_INTR	0x40288A50	FULL	Interrupt
DW0_CH_STRUCT41_INTR_SET	0x40288A54	FULL	Interrupt set
DW0_CH_STRUCT41_INTR_MASK	0x40288A58	FULL	Interrupt mask
DW0_CH_STRUCT41_INTR_MASKED	0x40288A5C	FULL	Interrupt masked
DW0_CH_STRUCT41_SRAM_DATA0	0x40288A60	FULL	SRAM data 0
DW0_CH_STRUCT41_SRAM_DATA1	0x40288A64	FULL	SRAM data 1
DW0_CH_STRUCT41_TR_CMD	0x40288A68	FULL	Channel software trigger

8.1.1.43 CH_STRUCT 42

Register Name	Address	Permission	Description
DW0_CH_STRUCT42_CH_CTL	0x40288A80	FULL	Channel control
DW0_CH_STRUCT42_CH_STATUS	0x40288A84	FULL	Channel status
DW0_CH_STRUCT42_CH_IDX	0x40288A88	FULL	Channel current indices
DW0_CH_STRUCT42_CH_CURR_PTR	0x40288A8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT42_INTR	0x40288A90	FULL	Interrupt
DW0_CH_STRUCT42_INTR_SET	0x40288A94	FULL	Interrupt set
DW0_CH_STRUCT42_INTR_MASK	0x40288A98	FULL	Interrupt mask
DW0_CH_STRUCT42_INTR_MASKED	0x40288A9C	FULL	Interrupt masked
DW0_CH_STRUCT42_SRAM_DATA0	0x40288AA0	FULL	SRAM data 0
DW0_CH_STRUCT42_SRAM_DATA1	0x40288AA4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT42_TR_CMD	0x40288AA8	FULL	Channel software trigger

8.1.1.44 CH_STRUCT 43

Register Name	Address	Permission	Description
DW0_CH_STRUCT43_CH_CTL	0x40288AC0	FULL	Channel control
DW0_CH_STRUCT43_CH_STATUS	0x40288AC4	FULL	Channel status
DW0_CH_STRUCT43_CH_IDX	0x40288AC8	FULL	Channel current indices
DW0_CH_STRUCT43_CH_CURR_PTR	0x40288ACC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT43_INTR	0x40288AD0	FULL	Interrupt
DW0_CH_STRUCT43_INTR_SET	0x40288AD4	FULL	Interrupt set
DW0_CH_STRUCT43_INTR_MASK	0x40288AD8	FULL	Interrupt mask
DW0_CH_STRUCT43_INTR_MASKED	0x40288ADC	FULL	Interrupt masked
DW0_CH_STRUCT43_SRAM_DATA0	0x40288AE0	FULL	SRAM data 0
DW0_CH_STRUCT43_SRAM_DATA1	0x40288AE4	FULL	SRAM data 1
DW0_CH_STRUCT43_TR_CMD	0x40288AE8	FULL	Channel software trigger

8.1.1.45 CH_STRUCT 44

Register Name	Address	Permission	Description
DW0_CH_STRUCT44_CH_CTL	0x40288B00	FULL	Channel control
DW0_CH_STRUCT44_CH_STATUS	0x40288B04	FULL	Channel status
DW0_CH_STRUCT44_CH_IDX	0x40288B08	FULL	Channel current indices
DW0_CH_STRUCT44_CH_CURR_PTR	0x40288B0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT44_INTR	0x40288B10	FULL	Interrupt
DW0_CH_STRUCT44_INTR_SET	0x40288B14	FULL	Interrupt set
DW0_CH_STRUCT44_INTR_MASK	0x40288B18	FULL	Interrupt mask
DW0_CH_STRUCT44_INTR_MASKED	0x40288B1C	FULL	Interrupt masked
DW0_CH_STRUCT44_SRAM_DATA0	0x40288B20	FULL	SRAM data 0
DW0_CH_STRUCT44_SRAM_DATA1	0x40288B24	FULL	SRAM data 1
DW0_CH_STRUCT44_TR_CMD	0x40288B28	FULL	Channel software trigger

8.1.1.46 CH_STRUCT 45

Register Name	Address	Permission	Description
DW0_CH_STRUCT45_CH_CTL	0x40288B40	FULL	Channel control
DW0_CH_STRUCT45_CH_STATUS	0x40288B44	FULL	Channel status
DW0_CH_STRUCT45_CH_IDX	0x40288B48	FULL	Channel current indices
DW0_CH_STRUCT45_CH_CURR_PTR	0x40288B4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT45_INTR	0x40288B50	FULL	Interrupt
DW0_CH_STRUCT45_INTR_SET	0x40288B54	FULL	Interrupt set
DW0_CH_STRUCT45_INTR_MASK	0x40288B58	FULL	Interrupt mask
DW0_CH_STRUCT45_INTR_MASKED	0x40288B5C	FULL	Interrupt masked
DW0_CH_STRUCT45_SRAM_DATA0	0x40288B60	FULL	SRAM data 0
DW0_CH_STRUCT45_SRAM_DATA1	0x40288B64	FULL	SRAM data 1
DW0_CH_STRUCT45_TR_CMD	0x40288B68	FULL	Channel software trigger

8.1.1.47 CH_STRUCT 46

Register Name	Address	Permission	Description
DW0_CH_STRUCT46_CH_CTL	0x40288B80	FULL	Channel control
DW0_CH_STRUCT46_CH_STATUS	0x40288B84	FULL	Channel status
DW0_CH_STRUCT46_CH_IDX	0x40288B88	FULL	Channel current indices
DW0_CH_STRUCT46_CH_CURR_PTR	0x40288B8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT46_INTR	0x40288B90	FULL	Interrupt
DW0_CH_STRUCT46_INTR_SET	0x40288B94	FULL	Interrupt set
DW0_CH_STRUCT46_INTR_MASK	0x40288B98	FULL	Interrupt mask
DW0_CH_STRUCT46_INTR_MASKED	0x40288B9C	FULL	Interrupt masked
DW0_CH_STRUCT46_SRAM_DATA0	0x40288BA0	FULL	SRAM data 0
DW0_CH_STRUCT46_SRAM_DATA1	0x40288BA4	FULL	SRAM data 1
DW0_CH_STRUCT46_TR_CMD	0x40288BA8	FULL	Channel software trigger

8.1.1.48 CH_STRUCT 47

Register Name	Address	Permission	Description
DW0_CH_STRUCT47_CH_CTL	0x40288BC0	FULL	Channel control
DW0_CH_STRUCT47_CH_STATUS	0x40288BC4	FULL	Channel status
DW0_CH_STRUCT47_CH_IDX	0x40288BC8	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT47_CH_CURR_PTR	0x40288BCC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT47_INTR	0x40288BD0	FULL	Interrupt
DW0_CH_STRUCT47_INTR_SET	0x40288BD4	FULL	Interrupt set
DW0_CH_STRUCT47_INTR_MASK	0x40288BD8	FULL	Interrupt mask
DW0_CH_STRUCT47_INTR_MASKED	0x40288BDC	FULL	Interrupt masked
DW0_CH_STRUCT47_SRAM_DATA0	0x40288BE0	FULL	SRAM data 0
DW0_CH_STRUCT47_SRAM_DATA1	0x40288BE4	FULL	SRAM data 1
DW0_CH_STRUCT47_TR_CMD	0x40288BE8	FULL	Channel software trigger

8.1.1.49 CH_STRUCT 48

Register Name	Address	Permission	Description
DW0_CH_STRUCT48_CH_CTL	0x40288C00	FULL	Channel control
DW0_CH_STRUCT48_CH_STATUS	0x40288C04	FULL	Channel status
DW0_CH_STRUCT48_CH_IDX	0x40288C08	FULL	Channel current indices
DW0_CH_STRUCT48_CH_CURR_PTR	0x40288C0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT48_INTR	0x40288C10	FULL	Interrupt
DW0_CH_STRUCT48_INTR_SET	0x40288C14	FULL	Interrupt set
DW0_CH_STRUCT48_INTR_MASK	0x40288C18	FULL	Interrupt mask
DW0_CH_STRUCT48_INTR_MASKED	0x40288C1C	FULL	Interrupt masked
DW0_CH_STRUCT48_SRAM_DATA0	0x40288C20	FULL	SRAM data 0
DW0_CH_STRUCT48_SRAM_DATA1	0x40288C24	FULL	SRAM data 1
DW0_CH_STRUCT48_TR_CMD	0x40288C28	FULL	Channel software trigger

8.1.1.50 CH_STRUCT 49

Register Name	Address	Permission	Description
DW0_CH_STRUCT49_CH_CTL	0x40288C40	FULL	Channel control
DW0_CH_STRUCT49_CH_STATUS	0x40288C44	FULL	Channel status
DW0_CH_STRUCT49_CH_IDX	0x40288C48	FULL	Channel current indices
DW0_CH_STRUCT49_CH_CURR_PTR	0x40288C4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT49_INTR	0x40288C50	FULL	Interrupt
DW0_CH_STRUCT49_INTR_SET	0x40288C54	FULL	Interrupt set
DW0_CH_STRUCT49_INTR_MASK	0x40288C58	FULL	Interrupt mask
DW0_CH_STRUCT49_INTR_MASKED	0x40288C5C	FULL	Interrupt masked
DW0_CH_STRUCT49_SRAM_DATA0	0x40288C60	FULL	SRAM data 0
DW0_CH_STRUCT49_SRAM_DATA1	0x40288C64	FULL	SRAM data 1
DW0_CH_STRUCT49_TR_CMD	0x40288C68	FULL	Channel software trigger

8.1.1.51 CH_STRUCT 50

Register Name	Address	Permission	Description
DW0_CH_STRUCT50_CH_CTL	0x40288C80	FULL	Channel control
DW0_CH_STRUCT50_CH_STATUS	0x40288C84	FULL	Channel status
DW0_CH_STRUCT50_CH_IDX	0x40288C88	FULL	Channel current indices
DW0_CH_STRUCT50_CH_CURR_PTR	0x40288C8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT50_INTR	0x40288C90	FULL	Interrupt
DW0_CH_STRUCT50_INTR_SET	0x40288C94	FULL	Interrupt set
DW0_CH_STRUCT50_INTR_MASK	0x40288C98	FULL	Interrupt mask
DW0_CH_STRUCT50_INTR_MASKED	0x40288C9C	FULL	Interrupt masked
DW0_CH_STRUCT50_SRAM_DATA0	0x40288CA0	FULL	SRAM data 0
DW0_CH_STRUCT50_SRAM_DATA1	0x40288CA4	FULL	SRAM data 1
DW0_CH_STRUCT50_TR_CMD	0x40288CA8	FULL	Channel software trigger

8.1.1.52 CH_STRUCT 51

Register Name	Address	Permission	Description
DW0_CH_STRUCT51_CH_CTL	0x40288CC0	FULL	Channel control
DW0_CH_STRUCT51_CH_STATUS	0x40288CC4	FULL	Channel status
DW0_CH_STRUCT51_CH_IDX	0x40288CC8	FULL	Channel current indices
DW0_CH_STRUCT51_CH_CURR_PTR	0x40288CCC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT51_INTR	0x40288CD0	FULL	Interrupt
DW0_CH_STRUCT51_INTR_SET	0x40288CD4	FULL	Interrupt set
DW0_CH_STRUCT51_INTR_MASK	0x40288CD8	FULL	Interrupt mask
DW0_CH_STRUCT51_INTR_MASKED	0x40288CDC	FULL	Interrupt masked
DW0_CH_STRUCT51_SRAM_DATA0	0x40288CE0	FULL	SRAM data 0
DW0_CH_STRUCT51_SRAM_DATA1	0x40288CE4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT51_TR_CMD	0x40288CE8	FULL	Channel software trigger

8.1.1.53 CH_STRUCT 52

Register Name	Address	Permission	Description
DW0_CH_STRUCT52_CH_CTL	0x40288D00	FULL	Channel control
DW0_CH_STRUCT52_CH_STATUS	0x40288D04	FULL	Channel status
DW0_CH_STRUCT52_CH_IDX	0x40288D08	FULL	Channel current indices
DW0_CH_STRUCT52_CH_CURR_PTR	0x40288D0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT52_INTR	0x40288D10	FULL	Interrupt
DW0_CH_STRUCT52_INTR_SET	0x40288D14	FULL	Interrupt set
DW0_CH_STRUCT52_INTR_MASK	0x40288D18	FULL	Interrupt mask
DW0_CH_STRUCT52_INTR_MASKED	0x40288D1C	FULL	Interrupt masked
DW0_CH_STRUCT52_SRAM_DATA0	0x40288D20	FULL	SRAM data 0
DW0_CH_STRUCT52_SRAM_DATA1	0x40288D24	FULL	SRAM data 1
DW0_CH_STRUCT52_TR_CMD	0x40288D28	FULL	Channel software trigger

8.1.1.54 CH_STRUCT 53

Register Name	Address	Permission	Description
DW0_CH_STRUCT53_CH_CTL	0x40288D40	FULL	Channel control
DW0_CH_STRUCT53_CH_STATUS	0x40288D44	FULL	Channel status
DW0_CH_STRUCT53_CH_IDX	0x40288D48	FULL	Channel current indices
DW0_CH_STRUCT53_CH_CURR_PTR	0x40288D4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT53_INTR	0x40288D50	FULL	Interrupt
DW0_CH_STRUCT53_INTR_SET	0x40288D54	FULL	Interrupt set
DW0_CH_STRUCT53_INTR_MASK	0x40288D58	FULL	Interrupt mask
DW0_CH_STRUCT53_INTR_MASKED	0x40288D5C	FULL	Interrupt masked
DW0_CH_STRUCT53_SRAM_DATA0	0x40288D60	FULL	SRAM data 0
DW0_CH_STRUCT53_SRAM_DATA1	0x40288D64	FULL	SRAM data 1
DW0_CH_STRUCT53_TR_CMD	0x40288D68	FULL	Channel software trigger

8.1.1.55 CH_STRUCT 54

Register Name	Address	Permission	Description
DW0_CH_STRUCT54_CH_CTL	0x40288D80	FULL	Channel control
DW0_CH_STRUCT54_CH_STATUS	0x40288D84	FULL	Channel status
DW0_CH_STRUCT54_CH_IDX	0x40288D88	FULL	Channel current indices
DW0_CH_STRUCT54_CH_CURR_PTR	0x40288D8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT54_INTR	0x40288D90	FULL	Interrupt
DW0_CH_STRUCT54_INTR_SET	0x40288D94	FULL	Interrupt set
DW0_CH_STRUCT54_INTR_MASK	0x40288D98	FULL	Interrupt mask
DW0_CH_STRUCT54_INTR_MASKED	0x40288D9C	FULL	Interrupt masked
DW0_CH_STRUCT54_SRAM_DATA0	0x40288DA0	FULL	SRAM data 0
DW0_CH_STRUCT54_SRAM_DATA1	0x40288DA4	FULL	SRAM data 1
DW0_CH_STRUCT54_TR_CMD	0x40288DA8	FULL	Channel software trigger

8.1.1.56 CH_STRUCT 55

Register Name	Address	Permission	Description
DW0_CH_STRUCT55_CH_CTL	0x40288DC0	FULL	Channel control
DW0_CH_STRUCT55_CH_STATUS	0x40288DC4	FULL	Channel status
DW0_CH_STRUCT55_CH_IDX	0x40288DC8	FULL	Channel current indices
DW0_CH_STRUCT55_CH_CURR_PTR	0x40288DCC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT55_INTR	0x40288DD0	FULL	Interrupt
DW0_CH_STRUCT55_INTR_SET	0x40288DD4	FULL	Interrupt set
DW0_CH_STRUCT55_INTR_MASK	0x40288DD8	FULL	Interrupt mask
DW0_CH_STRUCT55_INTR_MASKED	0x40288DDC	FULL	Interrupt masked
DW0_CH_STRUCT55_SRAM_DATA0	0x40288DE0	FULL	SRAM data 0
DW0_CH_STRUCT55_SRAM_DATA1	0x40288DE4	FULL	SRAM data 1
DW0_CH_STRUCT55_TR_CMD	0x40288DE8	FULL	Channel software trigger

8.1.1.57 CH_STRUCT 56

Register Name	Address	Permission	Description
DW0_CH_STRUCT56_CH_CTL	0x40288E00	FULL	Channel control
DW0_CH_STRUCT56_CH_STATUS	0x40288E04	FULL	Channel status
DW0_CH_STRUCT56_CH_IDX	0x40288E08	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT56_CH_CURR_PTR	0x40288E0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT56_INTR	0x40288E10	FULL	Interrupt
DW0_CH_STRUCT56_INTR_SET	0x40288E14	FULL	Interrupt set
DW0_CH_STRUCT56_INTR_MASK	0x40288E18	FULL	Interrupt mask
DW0_CH_STRUCT56_INTR_MASKED	0x40288E1C	FULL	Interrupt masked
DW0_CH_STRUCT56_SRAM_DATA0	0x40288E20	FULL	SRAM data 0
DW0_CH_STRUCT56_SRAM_DATA1	0x40288E24	FULL	SRAM data 1
DW0_CH_STRUCT56_TR_CMD	0x40288E28	FULL	Channel software trigger

8.1.1.58 CH_STRUCT 57

Register Name	Address	Permission	Description
DW0_CH_STRUCT57_CH_CTL	0x40288E40	FULL	Channel control
DW0_CH_STRUCT57_CH_STATUS	0x40288E44	FULL	Channel status
DW0_CH_STRUCT57_CH_IDX	0x40288E48	FULL	Channel current indices
DW0_CH_STRUCT57_CH_CURR_PTR	0x40288E4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT57_INTR	0x40288E50	FULL	Interrupt
DW0_CH_STRUCT57_INTR_SET	0x40288E54	FULL	Interrupt set
DW0_CH_STRUCT57_INTR_MASK	0x40288E58	FULL	Interrupt mask
DW0_CH_STRUCT57_INTR_MASKED	0x40288E5C	FULL	Interrupt masked
DW0_CH_STRUCT57_SRAM_DATA0	0x40288E60	FULL	SRAM data 0
DW0_CH_STRUCT57_SRAM_DATA1	0x40288E64	FULL	SRAM data 1
DW0_CH_STRUCT57_TR_CMD	0x40288E68	FULL	Channel software trigger

8.1.1.59 CH_STRUCT 58

Register Name	Address	Permission	Description
DW0_CH_STRUCT58_CH_CTL	0x40288E80	FULL	Channel control
DW0_CH_STRUCT58_CH_STATUS	0x40288E84	FULL	Channel status
DW0_CH_STRUCT58_CH_IDX	0x40288E88	FULL	Channel current indices
DW0_CH_STRUCT58_CH_CURR_PTR	0x40288E8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT58_INTR	0x40288E90	FULL	Interrupt
DW0_CH_STRUCT58_INTR_SET	0x40288E94	FULL	Interrupt set
DW0_CH_STRUCT58_INTR_MASK	0x40288E98	FULL	Interrupt mask
DW0_CH_STRUCT58_INTR_MASKED	0x40288E9C	FULL	Interrupt masked
DW0_CH_STRUCT58_SRAM_DATA0	0x40288EA0	FULL	SRAM data 0
DW0_CH_STRUCT58_SRAM_DATA1	0x40288EA4	FULL	SRAM data 1
DW0_CH_STRUCT58_TR_CMD	0x40288EA8	FULL	Channel software trigger

8.1.1.60 CH_STRUCT 59

Register Name	Address	Permission	Description
DW0_CH_STRUCT59_CH_CTL	0x40288EC0	FULL	Channel control
DW0_CH_STRUCT59_CH_STATUS	0x40288EC4	FULL	Channel status
DW0_CH_STRUCT59_CH_IDX	0x40288EC8	FULL	Channel current indices
DW0_CH_STRUCT59_CH_CURR_PTR	0x40288ECC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT59_INTR	0x40288ED0	FULL	Interrupt
DW0_CH_STRUCT59_INTR_SET	0x40288ED4	FULL	Interrupt set
DW0_CH_STRUCT59_INTR_MASK	0x40288ED8	FULL	Interrupt mask
DW0_CH_STRUCT59_INTR_MASKED	0x40288EDC	FULL	Interrupt masked
DW0_CH_STRUCT59_SRAM_DATA0	0x40288EE0	FULL	SRAM data 0
DW0_CH_STRUCT59_SRAM_DATA1	0x40288EE4	FULL	SRAM data 1
DW0_CH_STRUCT59_TR_CMD	0x40288EE8	FULL	Channel software trigger

8.1.1.61 CH_STRUCT 60

Register Name	Address	Permission	Description
DW0_CH_STRUCT60_CH_CTL	0x40288F00	FULL	Channel control
DW0_CH_STRUCT60_CH_STATUS	0x40288F04	FULL	Channel status
DW0_CH_STRUCT60_CH_IDX	0x40288F08	FULL	Channel current indices
DW0_CH_STRUCT60_CH_CURR_PTR	0x40288F0C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT60_INTR	0x40288F10	FULL	Interrupt
DW0_CH_STRUCT60_INTR_SET	0x40288F14	FULL	Interrupt set
DW0_CH_STRUCT60_INTR_MASK	0x40288F18	FULL	Interrupt mask
DW0_CH_STRUCT60_INTR_MASKED	0x40288F1C	FULL	Interrupt masked
DW0_CH_STRUCT60_SRAM_DATA0	0x40288F20	FULL	SRAM data 0
DW0_CH_STRUCT60_SRAM_DATA1	0x40288F24	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT60_TR_CMD	0x40288F28	FULL	Channel software trigger

8.1.1.62 CH_STRUCT 61

Register Name	Address	Permission	Description
DW0_CH_STRUCT61_CH_CTL	0x40288F40	FULL	Channel control
DW0_CH_STRUCT61_CH_STATUS	0x40288F44	FULL	Channel status
DW0_CH_STRUCT61_CH_IDX	0x40288F48	FULL	Channel current indices
DW0_CH_STRUCT61_CH_CURR_PTR	0x40288F4C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT61_INTR	0x40288F50	FULL	Interrupt
DW0_CH_STRUCT61_INTR_SET	0x40288F54	FULL	Interrupt set
DW0_CH_STRUCT61_INTR_MASK	0x40288F58	FULL	Interrupt mask
DW0_CH_STRUCT61_INTR_MASKED	0x40288F5C	FULL	Interrupt masked
DW0_CH_STRUCT61_SRAM_DATA0	0x40288F60	FULL	SRAM data 0
DW0_CH_STRUCT61_SRAM_DATA1	0x40288F64	FULL	SRAM data 1
DW0_CH_STRUCT61_TR_CMD	0x40288F68	FULL	Channel software trigger

8.1.1.63 CH_STRUCT 62

Register Name	Address	Permission	Description
DW0_CH_STRUCT62_CH_CTL	0x40288F80	FULL	Channel control
DW0_CH_STRUCT62_CH_STATUS	0x40288F84	FULL	Channel status
DW0_CH_STRUCT62_CH_IDX	0x40288F88	FULL	Channel current indices
DW0_CH_STRUCT62_CH_CURR_PTR	0x40288F8C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT62_INTR	0x40288F90	FULL	Interrupt
DW0_CH_STRUCT62_INTR_SET	0x40288F94	FULL	Interrupt set
DW0_CH_STRUCT62_INTR_MASK	0x40288F98	FULL	Interrupt mask
DW0_CH_STRUCT62_INTR_MASKED	0x40288F9C	FULL	Interrupt masked
DW0_CH_STRUCT62_SRAM_DATA0	0x40288FA0	FULL	SRAM data 0
DW0_CH_STRUCT62_SRAM_DATA1	0x40288FA4	FULL	SRAM data 1
DW0_CH_STRUCT62_TR_CMD	0x40288FA8	FULL	Channel software trigger

8.1.1.64 CH_STRUCT 63

Register Name	Address	Permission	Description
DW0_CH_STRUCT63_CH_CTL	0x40288FC0	FULL	Channel control
DW0_CH_STRUCT63_CH_STATUS	0x40288FC4	FULL	Channel status
DW0_CH_STRUCT63_CH_IDX	0x40288FC8	FULL	Channel current indices
DW0_CH_STRUCT63_CH_CURR_PTR	0x40288FCC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT63_INTR	0x40288FD0	FULL	Interrupt
DW0_CH_STRUCT63_INTR_SET	0x40288FD4	FULL	Interrupt set
DW0_CH_STRUCT63_INTR_MASK	0x40288FD8	FULL	Interrupt mask
DW0_CH_STRUCT63_INTR_MASKED	0x40288FDC	FULL	Interrupt masked
DW0_CH_STRUCT63_SRAM_DATA0	0x40288FE0	FULL	SRAM data 0
DW0_CH_STRUCT63_SRAM_DATA1	0x40288FE4	FULL	SRAM data 1
DW0_CH_STRUCT63_TR_CMD	0x40288FE8	FULL	Channel software trigger

8.1.1.65 CH_STRUCT 64

Register Name	Address	Permission	Description
DW0_CH_STRUCT64_CH_CTL	0x40289000	FULL	Channel control
DW0_CH_STRUCT64_CH_STATUS	0x40289004	FULL	Channel status
DW0_CH_STRUCT64_CH_IDX	0x40289008	FULL	Channel current indices
DW0_CH_STRUCT64_CH_CURR_PTR	0x4028900C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT64_INTR	0x40289010	FULL	Interrupt
DW0_CH_STRUCT64_INTR_SET	0x40289014	FULL	Interrupt set
DW0_CH_STRUCT64_INTR_MASK	0x40289018	FULL	Interrupt mask
DW0_CH_STRUCT64_INTR_MASKED	0x4028901C	FULL	Interrupt masked
DW0_CH_STRUCT64_SRAM_DATA0	0x40289020	FULL	SRAM data 0
DW0_CH_STRUCT64_SRAM_DATA1	0x40289024	FULL	SRAM data 1
DW0_CH_STRUCT64_TR_CMD	0x40289028	FULL	Channel software trigger

8.1.1.66 CH_STRUCT 65

Register Name	Address	Permission	Description
DW0_CH_STRUCT65_CH_CTL	0x40289040	FULL	Channel control
DW0_CH_STRUCT65_CH_STATUS	0x40289044	FULL	Channel status
DW0_CH_STRUCT65_CH_IDX	0x40289048	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT65_CH_CURR_PTR	0x4028904C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT65_INTR	0x40289050	FULL	Interrupt
DW0_CH_STRUCT65_INTR_SET	0x40289054	FULL	Interrupt set
DW0_CH_STRUCT65_INTR_MASK	0x40289058	FULL	Interrupt mask
DW0_CH_STRUCT65_INTR_MASKED	0x4028905C	FULL	Interrupt masked
DW0_CH_STRUCT65_SRAM_DATA0	0x40289060	FULL	SRAM data 0
DW0_CH_STRUCT65_SRAM_DATA1	0x40289064	FULL	SRAM data 1
DW0_CH_STRUCT65_TR_CMD	0x40289068	FULL	Channel software trigger

8.1.1.67 CH_STRUCT 66

Register Name	Address	Permission	Description
DW0_CH_STRUCT66_CH_CTL	0x40289080	FULL	Channel control
DW0_CH_STRUCT66_CH_STATUS	0x40289084	FULL	Channel status
DW0_CH_STRUCT66_CH_IDX	0x40289088	FULL	Channel current indices
DW0_CH_STRUCT66_CH_CURR_PTR	0x4028908C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT66_INTR	0x40289090	FULL	Interrupt
DW0_CH_STRUCT66_INTR_SET	0x40289094	FULL	Interrupt set
DW0_CH_STRUCT66_INTR_MASK	0x40289098	FULL	Interrupt mask
DW0_CH_STRUCT66_INTR_MASKED	0x4028909C	FULL	Interrupt masked
DW0_CH_STRUCT66_SRAM_DATA0	0x402890A0	FULL	SRAM data 0
DW0_CH_STRUCT66_SRAM_DATA1	0x402890A4	FULL	SRAM data 1
DW0_CH_STRUCT66_TR_CMD	0x402890A8	FULL	Channel software trigger

8.1.1.68 CH_STRUCT 67

Register Name	Address	Permission	Description
DW0_CH_STRUCT67_CH_CTL	0x402890C0	FULL	Channel control
DW0_CH_STRUCT67_CH_STATUS	0x402890C4	FULL	Channel status
DW0_CH_STRUCT67_CH_IDX	0x402890C8	FULL	Channel current indices
DW0_CH_STRUCT67_CH_CURR_PTR	0x402890CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT67_INTR	0x402890D0	FULL	Interrupt
DW0_CH_STRUCT67_INTR_SET	0x402890D4	FULL	Interrupt set
DW0_CH_STRUCT67_INTR_MASK	0x402890D8	FULL	Interrupt mask
DW0_CH_STRUCT67_INTR_MASKED	0x402890DC	FULL	Interrupt masked
DW0_CH_STRUCT67_SRAM_DATA0	0x402890E0	FULL	SRAM data 0
DW0_CH_STRUCT67_SRAM_DATA1	0x402890E4	FULL	SRAM data 1
DW0_CH_STRUCT67_TR_CMD	0x402890E8	FULL	Channel software trigger

8.1.1.69 CH_STRUCT 68

Register Name	Address	Permission	Description
DW0_CH_STRUCT68_CH_CTL	0x40289100	FULL	Channel control
DW0_CH_STRUCT68_CH_STATUS	0x40289104	FULL	Channel status
DW0_CH_STRUCT68_CH_IDX	0x40289108	FULL	Channel current indices
DW0_CH_STRUCT68_CH_CURR_PTR	0x4028910C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT68_INTR	0x40289110	FULL	Interrupt
DW0_CH_STRUCT68_INTR_SET	0x40289114	FULL	Interrupt set
DW0_CH_STRUCT68_INTR_MASK	0x40289118	FULL	Interrupt mask
DW0_CH_STRUCT68_INTR_MASKED	0x4028911C	FULL	Interrupt masked
DW0_CH_STRUCT68_SRAM_DATA0	0x40289120	FULL	SRAM data 0
DW0_CH_STRUCT68_SRAM_DATA1	0x40289124	FULL	SRAM data 1
DW0_CH_STRUCT68_TR_CMD	0x40289128	FULL	Channel software trigger

8.1.1.70 CH_STRUCT 69

Register Name	Address	Permission	Description
DW0_CH_STRUCT69_CH_CTL	0x40289140	FULL	Channel control
DW0_CH_STRUCT69_CH_STATUS	0x40289144	FULL	Channel status
DW0_CH_STRUCT69_CH_IDX	0x40289148	FULL	Channel current indices
DW0_CH_STRUCT69_CH_CURR_PTR	0x4028914C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT69_INTR	0x40289150	FULL	Interrupt
DW0_CH_STRUCT69_INTR_SET	0x40289154	FULL	Interrupt set
DW0_CH_STRUCT69_INTR_MASK	0x40289158	FULL	Interrupt mask
DW0_CH_STRUCT69_INTR_MASKED	0x4028915C	FULL	Interrupt masked
DW0_CH_STRUCT69_SRAM_DATA0	0x40289160	FULL	SRAM data 0
DW0_CH_STRUCT69_SRAM_DATA1	0x40289164	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT69_TR_CMD	0x40289168	FULL	Channel software trigger

8.1.1.71 CH_STRUCT 70

Register Name	Address	Permission	Description
DW0_CH_STRUCT70_CH_CTL	0x40289180	FULL	Channel control
DW0_CH_STRUCT70_CH_STATUS	0x40289184	FULL	Channel status
DW0_CH_STRUCT70_CH_IDX	0x40289188	FULL	Channel current indices
DW0_CH_STRUCT70_CH_CURR_PTR	0x4028918C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT70_INTR	0x40289190	FULL	Interrupt
DW0_CH_STRUCT70_INTR_SET	0x40289194	FULL	Interrupt set
DW0_CH_STRUCT70_INTR_MASK	0x40289198	FULL	Interrupt mask
DW0_CH_STRUCT70_INTR_MASKED	0x4028919C	FULL	Interrupt masked
DW0_CH_STRUCT70_SRAM_DATA0	0x402891A0	FULL	SRAM data 0
DW0_CH_STRUCT70_SRAM_DATA1	0x402891A4	FULL	SRAM data 1
DW0_CH_STRUCT70_TR_CMD	0x402891A8	FULL	Channel software trigger

8.1.1.72 CH_STRUCT 71

Register Name	Address	Permission	Description
DW0_CH_STRUCT71_CH_CTL	0x402891C0	FULL	Channel control
DW0_CH_STRUCT71_CH_STATUS	0x402891C4	FULL	Channel status
DW0_CH_STRUCT71_CH_IDX	0x402891C8	FULL	Channel current indices
DW0_CH_STRUCT71_CH_CURR_PTR	0x402891CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT71_INTR	0x402891D0	FULL	Interrupt
DW0_CH_STRUCT71_INTR_SET	0x402891D4	FULL	Interrupt set
DW0_CH_STRUCT71_INTR_MASK	0x402891D8	FULL	Interrupt mask
DW0_CH_STRUCT71_INTR_MASKED	0x402891DC	FULL	Interrupt masked
DW0_CH_STRUCT71_SRAM_DATA0	0x402891E0	FULL	SRAM data 0
DW0_CH_STRUCT71_SRAM_DATA1	0x402891E4	FULL	SRAM data 1
DW0_CH_STRUCT71_TR_CMD	0x402891E8	FULL	Channel software trigger

8.1.1.73 CH_STRUCT 72

Register Name	Address	Permission	Description
DW0_CH_STRUCT72_CH_CTL	0x40289200	FULL	Channel control
DW0_CH_STRUCT72_CH_STATUS	0x40289204	FULL	Channel status
DW0_CH_STRUCT72_CH_IDX	0x40289208	FULL	Channel current indices
DW0_CH_STRUCT72_CH_CURR_PTR	0x4028920C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT72_INTR	0x40289210	FULL	Interrupt
DW0_CH_STRUCT72_INTR_SET	0x40289214	FULL	Interrupt set
DW0_CH_STRUCT72_INTR_MASK	0x40289218	FULL	Interrupt mask
DW0_CH_STRUCT72_INTR_MASKED	0x4028921C	FULL	Interrupt masked
DW0_CH_STRUCT72_SRAM_DATA0	0x40289220	FULL	SRAM data 0
DW0_CH_STRUCT72_SRAM_DATA1	0x40289224	FULL	SRAM data 1
DW0_CH_STRUCT72_TR_CMD	0x40289228	FULL	Channel software trigger

8.1.1.74 CH_STRUCT 73

Register Name	Address	Permission	Description
DW0_CH_STRUCT73_CH_CTL	0x40289240	FULL	Channel control
DW0_CH_STRUCT73_CH_STATUS	0x40289244	FULL	Channel status
DW0_CH_STRUCT73_CH_IDX	0x40289248	FULL	Channel current indices
DW0_CH_STRUCT73_CH_CURR_PTR	0x4028924C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT73_INTR	0x40289250	FULL	Interrupt
DW0_CH_STRUCT73_INTR_SET	0x40289254	FULL	Interrupt set
DW0_CH_STRUCT73_INTR_MASK	0x40289258	FULL	Interrupt mask
DW0_CH_STRUCT73_INTR_MASKED	0x4028925C	FULL	Interrupt masked
DW0_CH_STRUCT73_SRAM_DATA0	0x40289260	FULL	SRAM data 0
DW0_CH_STRUCT73_SRAM_DATA1	0x40289264	FULL	SRAM data 1
DW0_CH_STRUCT73_TR_CMD	0x40289268	FULL	Channel software trigger

8.1.1.75 CH_STRUCT 74

Register Name	Address	Permission	Description
DW0_CH_STRUCT74_CH_CTL	0x40289280	FULL	Channel control
DW0_CH_STRUCT74_CH_STATUS	0x40289284	FULL	Channel status
DW0_CH_STRUCT74_CH_IDX	0x40289288	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT74_CH_CURR_PTR	0x4028928C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT74_INTR	0x40289290	FULL	Interrupt
DW0_CH_STRUCT74_INTR_SET	0x40289294	FULL	Interrupt set
DW0_CH_STRUCT74_INTR_MASK	0x40289298	FULL	Interrupt mask
DW0_CH_STRUCT74_INTR_MASKED	0x4028929C	FULL	Interrupt masked
DW0_CH_STRUCT74_SRAM_DATA0	0x402892A0	FULL	SRAM data 0
DW0_CH_STRUCT74_SRAM_DATA1	0x402892A4	FULL	SRAM data 1
DW0_CH_STRUCT74_TR_CMD	0x402892A8	FULL	Channel software trigger

8.1.1.76 CH_STRUCT 75

Register Name	Address	Permission	Description
DW0_CH_STRUCT75_CH_CTL	0x402892C0	FULL	Channel control
DW0_CH_STRUCT75_CH_STATUS	0x402892C4	FULL	Channel status
DW0_CH_STRUCT75_CH_IDX	0x402892C8	FULL	Channel current indices
DW0_CH_STRUCT75_CH_CURR_PTR	0x402892CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT75_INTR	0x402892D0	FULL	Interrupt
DW0_CH_STRUCT75_INTR_SET	0x402892D4	FULL	Interrupt set
DW0_CH_STRUCT75_INTR_MASK	0x402892D8	FULL	Interrupt mask
DW0_CH_STRUCT75_INTR_MASKED	0x402892DC	FULL	Interrupt masked
DW0_CH_STRUCT75_SRAM_DATA0	0x402892E0	FULL	SRAM data 0
DW0_CH_STRUCT75_SRAM_DATA1	0x402892E4	FULL	SRAM data 1
DW0_CH_STRUCT75_TR_CMD	0x402892E8	FULL	Channel software trigger

8.1.1.77 CH_STRUCT 76

Register Name	Address	Permission	Description
DW0_CH_STRUCT76_CH_CTL	0x40289300	FULL	Channel control
DW0_CH_STRUCT76_CH_STATUS	0x40289304	FULL	Channel status
DW0_CH_STRUCT76_CH_IDX	0x40289308	FULL	Channel current indices
DW0_CH_STRUCT76_CH_CURR_PTR	0x4028930C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT76_INTR	0x40289310	FULL	Interrupt
DW0_CH_STRUCT76_INTR_SET	0x40289314	FULL	Interrupt set
DW0_CH_STRUCT76_INTR_MASK	0x40289318	FULL	Interrupt mask
DW0_CH_STRUCT76_INTR_MASKED	0x4028931C	FULL	Interrupt masked
DW0_CH_STRUCT76_SRAM_DATA0	0x40289320	FULL	SRAM data 0
DW0_CH_STRUCT76_SRAM_DATA1	0x40289324	FULL	SRAM data 1
DW0_CH_STRUCT76_TR_CMD	0x40289328	FULL	Channel software trigger

8.1.1.78 CH_STRUCT 77

Register Name	Address	Permission	Description
DW0_CH_STRUCT77_CH_CTL	0x40289340	FULL	Channel control
DW0_CH_STRUCT77_CH_STATUS	0x40289344	FULL	Channel status
DW0_CH_STRUCT77_CH_IDX	0x40289348	FULL	Channel current indices
DW0_CH_STRUCT77_CH_CURR_PTR	0x4028934C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT77_INTR	0x40289350	FULL	Interrupt
DW0_CH_STRUCT77_INTR_SET	0x40289354	FULL	Interrupt set
DW0_CH_STRUCT77_INTR_MASK	0x40289358	FULL	Interrupt mask
DW0_CH_STRUCT77_INTR_MASKED	0x4028935C	FULL	Interrupt masked
DW0_CH_STRUCT77_SRAM_DATA0	0x40289360	FULL	SRAM data 0
DW0_CH_STRUCT77_SRAM_DATA1	0x40289364	FULL	SRAM data 1
DW0_CH_STRUCT77_TR_CMD	0x40289368	FULL	Channel software trigger

8.1.1.79 CH_STRUCT 78

Register Name	Address	Permission	Description
DW0_CH_STRUCT78_CH_CTL	0x40289380	FULL	Channel control
DW0_CH_STRUCT78_CH_STATUS	0x40289384	FULL	Channel status
DW0_CH_STRUCT78_CH_IDX	0x40289388	FULL	Channel current indices
DW0_CH_STRUCT78_CH_CURR_PTR	0x4028938C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT78_INTR	0x40289390	FULL	Interrupt
DW0_CH_STRUCT78_INTR_SET	0x40289394	FULL	Interrupt set
DW0_CH_STRUCT78_INTR_MASK	0x40289398	FULL	Interrupt mask
DW0_CH_STRUCT78_INTR_MASKED	0x4028939C	FULL	Interrupt masked
DW0_CH_STRUCT78_SRAM_DATA0	0x402893A0	FULL	SRAM data 0
DW0_CH_STRUCT78_SRAM_DATA1	0x402893A4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT78_TR_CMD	0x402893A8	FULL	Channel software trigger

8.1.1.80 CH_STRUCT 79

Register Name	Address	Permission	Description
DW0_CH_STRUCT79_CH_CTL	0x402893C0	FULL	Channel control
DW0_CH_STRUCT79_CH_STATUS	0x402893C4	FULL	Channel status
DW0_CH_STRUCT79_CH_IDX	0x402893C8	FULL	Channel current indices
DW0_CH_STRUCT79_CH_CURR_PTR	0x402893CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT79_INTR	0x402893D0	FULL	Interrupt
DW0_CH_STRUCT79_INTR_SET	0x402893D4	FULL	Interrupt set
DW0_CH_STRUCT79_INTR_MASK	0x402893D8	FULL	Interrupt mask
DW0_CH_STRUCT79_INTR_MASKED	0x402893DC	FULL	Interrupt masked
DW0_CH_STRUCT79_SRAM_DATA0	0x402893E0	FULL	SRAM data 0
DW0_CH_STRUCT79_SRAM_DATA1	0x402893E4	FULL	SRAM data 1
DW0_CH_STRUCT79_TR_CMD	0x402893E8	FULL	Channel software trigger

8.1.1.81 CH_STRUCT 80

Register Name	Address	Permission	Description
DW0_CH_STRUCT80_CH_CTL	0x40289400	FULL	Channel control
DW0_CH_STRUCT80_CH_STATUS	0x40289404	FULL	Channel status
DW0_CH_STRUCT80_CH_IDX	0x40289408	FULL	Channel current indices
DW0_CH_STRUCT80_CH_CURR_PTR	0x4028940C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT80_INTR	0x40289410	FULL	Interrupt
DW0_CH_STRUCT80_INTR_SET	0x40289414	FULL	Interrupt set
DW0_CH_STRUCT80_INTR_MASK	0x40289418	FULL	Interrupt mask
DW0_CH_STRUCT80_INTR_MASKED	0x4028941C	FULL	Interrupt masked
DW0_CH_STRUCT80_SRAM_DATA0	0x40289420	FULL	SRAM data 0
DW0_CH_STRUCT80_SRAM_DATA1	0x40289424	FULL	SRAM data 1
DW0_CH_STRUCT80_TR_CMD	0x40289428	FULL	Channel software trigger

8.1.1.82 CH_STRUCT 81

Register Name	Address	Permission	Description
DW0_CH_STRUCT81_CH_CTL	0x40289440	FULL	Channel control
DW0_CH_STRUCT81_CH_STATUS	0x40289444	FULL	Channel status
DW0_CH_STRUCT81_CH_IDX	0x40289448	FULL	Channel current indices
DW0_CH_STRUCT81_CH_CURR_PTR	0x4028944C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT81_INTR	0x40289450	FULL	Interrupt
DW0_CH_STRUCT81_INTR_SET	0x40289454	FULL	Interrupt set
DW0_CH_STRUCT81_INTR_MASK	0x40289458	FULL	Interrupt mask
DW0_CH_STRUCT81_INTR_MASKED	0x4028945C	FULL	Interrupt masked
DW0_CH_STRUCT81_SRAM_DATA0	0x40289460	FULL	SRAM data 0
DW0_CH_STRUCT81_SRAM_DATA1	0x40289464	FULL	SRAM data 1
DW0_CH_STRUCT81_TR_CMD	0x40289468	FULL	Channel software trigger

8.1.1.83 CH_STRUCT 82

Register Name	Address	Permission	Description
DW0_CH_STRUCT82_CH_CTL	0x40289480	FULL	Channel control
DW0_CH_STRUCT82_CH_STATUS	0x40289484	FULL	Channel status
DW0_CH_STRUCT82_CH_IDX	0x40289488	FULL	Channel current indices
DW0_CH_STRUCT82_CH_CURR_PTR	0x4028948C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT82_INTR	0x40289490	FULL	Interrupt
DW0_CH_STRUCT82_INTR_SET	0x40289494	FULL	Interrupt set
DW0_CH_STRUCT82_INTR_MASK	0x40289498	FULL	Interrupt mask
DW0_CH_STRUCT82_INTR_MASKED	0x4028949C	FULL	Interrupt masked
DW0_CH_STRUCT82_SRAM_DATA0	0x402894A0	FULL	SRAM data 0
DW0_CH_STRUCT82_SRAM_DATA1	0x402894A4	FULL	SRAM data 1
DW0_CH_STRUCT82_TR_CMD	0x402894A8	FULL	Channel software trigger

8.1.1.84 CH_STRUCT 83

Register Name	Address	Permission	Description
DW0_CH_STRUCT83_CH_CTL	0x402894C0	FULL	Channel control
DW0_CH_STRUCT83_CH_STATUS	0x402894C4	FULL	Channel status
DW0_CH_STRUCT83_CH_IDX	0x402894C8	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT83_CH_CURR_PTR	0x402894CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT83_INTR	0x402894D0	FULL	Interrupt
DW0_CH_STRUCT83_INTR_SET	0x402894D4	FULL	Interrupt set
DW0_CH_STRUCT83_INTR_MASK	0x402894D8	FULL	Interrupt mask
DW0_CH_STRUCT83_INTR_MASKED	0x402894DC	FULL	Interrupt masked
DW0_CH_STRUCT83_SRAM_DATA0	0x402894E0	FULL	SRAM data 0
DW0_CH_STRUCT83_SRAM_DATA1	0x402894E4	FULL	SRAM data 1
DW0_CH_STRUCT83_TR_CMD	0x402894E8	FULL	Channel software trigger

8.1.1.85 CH_STRUCT 84

Register Name	Address	Permission	Description
DW0_CH_STRUCT84_CH_CTL	0x40289500	FULL	Channel control
DW0_CH_STRUCT84_CH_STATUS	0x40289504	FULL	Channel status
DW0_CH_STRUCT84_CH_IDX	0x40289508	FULL	Channel current indices
DW0_CH_STRUCT84_CH_CURR_PTR	0x4028950C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT84_INTR	0x40289510	FULL	Interrupt
DW0_CH_STRUCT84_INTR_SET	0x40289514	FULL	Interrupt set
DW0_CH_STRUCT84_INTR_MASK	0x40289518	FULL	Interrupt mask
DW0_CH_STRUCT84_INTR_MASKED	0x4028951C	FULL	Interrupt masked
DW0_CH_STRUCT84_SRAM_DATA0	0x40289520	FULL	SRAM data 0
DW0_CH_STRUCT84_SRAM_DATA1	0x40289524	FULL	SRAM data 1
DW0_CH_STRUCT84_TR_CMD	0x40289528	FULL	Channel software trigger

8.1.1.86 CH_STRUCT 85

Register Name	Address	Permission	Description
DW0_CH_STRUCT85_CH_CTL	0x40289540	FULL	Channel control
DW0_CH_STRUCT85_CH_STATUS	0x40289544	FULL	Channel status
DW0_CH_STRUCT85_CH_IDX	0x40289548	FULL	Channel current indices
DW0_CH_STRUCT85_CH_CURR_PTR	0x4028954C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT85_INTR	0x40289550	FULL	Interrupt
DW0_CH_STRUCT85_INTR_SET	0x40289554	FULL	Interrupt set
DW0_CH_STRUCT85_INTR_MASK	0x40289558	FULL	Interrupt mask
DW0_CH_STRUCT85_INTR_MASKED	0x4028955C	FULL	Interrupt masked
DW0_CH_STRUCT85_SRAM_DATA0	0x40289560	FULL	SRAM data 0
DW0_CH_STRUCT85_SRAM_DATA1	0x40289564	FULL	SRAM data 1
DW0_CH_STRUCT85_TR_CMD	0x40289568	FULL	Channel software trigger

8.1.1.87 CH_STRUCT 86

Register Name	Address	Permission	Description
DW0_CH_STRUCT86_CH_CTL	0x40289580	FULL	Channel control
DW0_CH_STRUCT86_CH_STATUS	0x40289584	FULL	Channel status
DW0_CH_STRUCT86_CH_IDX	0x40289588	FULL	Channel current indices
DW0_CH_STRUCT86_CH_CURR_PTR	0x4028958C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT86_INTR	0x40289590	FULL	Interrupt
DW0_CH_STRUCT86_INTR_SET	0x40289594	FULL	Interrupt set
DW0_CH_STRUCT86_INTR_MASK	0x40289598	FULL	Interrupt mask
DW0_CH_STRUCT86_INTR_MASKED	0x4028959C	FULL	Interrupt masked
DW0_CH_STRUCT86_SRAM_DATA0	0x402895A0	FULL	SRAM data 0
DW0_CH_STRUCT86_SRAM_DATA1	0x402895A4	FULL	SRAM data 1
DW0_CH_STRUCT86_TR_CMD	0x402895A8	FULL	Channel software trigger

8.1.1.88 CH_STRUCT 87

Register Name	Address	Permission	Description
DW0_CH_STRUCT87_CH_CTL	0x402895C0	FULL	Channel control
DW0_CH_STRUCT87_CH_STATUS	0x402895C4	FULL	Channel status
DW0_CH_STRUCT87_CH_IDX	0x402895C8	FULL	Channel current indices
DW0_CH_STRUCT87_CH_CURR_PTR	0x402895CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT87_INTR	0x402895D0	FULL	Interrupt
DW0_CH_STRUCT87_INTR_SET	0x402895D4	FULL	Interrupt set
DW0_CH_STRUCT87_INTR_MASK	0x402895D8	FULL	Interrupt mask
DW0_CH_STRUCT87_INTR_MASKED	0x402895DC	FULL	Interrupt masked
DW0_CH_STRUCT87_SRAM_DATA0	0x402895E0	FULL	SRAM data 0
DW0_CH_STRUCT87_SRAM_DATA1	0x402895E4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT87_TR_CMD	0x402895E8	FULL	Channel software trigger

8.1.1.89 CH_STRUCT 88

Register Name	Address	Permission	Description
DW0_CH_STRUCT88_CH_CTL	0x40289600	FULL	Channel control
DW0_CH_STRUCT88_CH_STATUS	0x40289604	FULL	Channel status
DW0_CH_STRUCT88_CH_IDX	0x40289608	FULL	Channel current indices
DW0_CH_STRUCT88_CH_CURR_PTR	0x4028960C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT88_INTR	0x40289610	FULL	Interrupt
DW0_CH_STRUCT88_INTR_SET	0x40289614	FULL	Interrupt set
DW0_CH_STRUCT88_INTR_MASK	0x40289618	FULL	Interrupt mask
DW0_CH_STRUCT88_INTR_MASKED	0x4028961C	FULL	Interrupt masked
DW0_CH_STRUCT88_SRAM_DATA0	0x40289620	FULL	SRAM data 0
DW0_CH_STRUCT88_SRAM_DATA1	0x40289624	FULL	SRAM data 1
DW0_CH_STRUCT88_TR_CMD	0x40289628	FULL	Channel software trigger

8.1.1.90 CH_STRUCT 89

Register Name	Address	Permission	Description
DW0_CH_STRUCT89_CH_CTL	0x40289640	FULL	Channel control
DW0_CH_STRUCT89_CH_STATUS	0x40289644	FULL	Channel status
DW0_CH_STRUCT89_CH_IDX	0x40289648	FULL	Channel current indices
DW0_CH_STRUCT89_CH_CURR_PTR	0x4028964C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT89_INTR	0x40289650	FULL	Interrupt
DW0_CH_STRUCT89_INTR_SET	0x40289654	FULL	Interrupt set
DW0_CH_STRUCT89_INTR_MASK	0x40289658	FULL	Interrupt mask
DW0_CH_STRUCT89_INTR_MASKED	0x4028965C	FULL	Interrupt masked
DW0_CH_STRUCT89_SRAM_DATA0	0x40289660	FULL	SRAM data 0
DW0_CH_STRUCT89_SRAM_DATA1	0x40289664	FULL	SRAM data 1
DW0_CH_STRUCT89_TR_CMD	0x40289668	FULL	Channel software trigger

8.1.1.91 CH_STRUCT 90

Register Name	Address	Permission	Description
DW0_CH_STRUCT90_CH_CTL	0x40289680	FULL	Channel control
DW0_CH_STRUCT90_CH_STATUS	0x40289684	FULL	Channel status
DW0_CH_STRUCT90_CH_IDX	0x40289688	FULL	Channel current indices
DW0_CH_STRUCT90_CH_CURR_PTR	0x4028968C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT90_INTR	0x40289690	FULL	Interrupt
DW0_CH_STRUCT90_INTR_SET	0x40289694	FULL	Interrupt set
DW0_CH_STRUCT90_INTR_MASK	0x40289698	FULL	Interrupt mask
DW0_CH_STRUCT90_INTR_MASKED	0x4028969C	FULL	Interrupt masked
DW0_CH_STRUCT90_SRAM_DATA0	0x402896A0	FULL	SRAM data 0
DW0_CH_STRUCT90_SRAM_DATA1	0x402896A4	FULL	SRAM data 1
DW0_CH_STRUCT90_TR_CMD	0x402896A8	FULL	Channel software trigger

8.1.1.92 CH_STRUCT 91

Register Name	Address	Permission	Description
DW0_CH_STRUCT91_CH_CTL	0x402896C0	FULL	Channel control
DW0_CH_STRUCT91_CH_STATUS	0x402896C4	FULL	Channel status
DW0_CH_STRUCT91_CH_IDX	0x402896C8	FULL	Channel current indices
DW0_CH_STRUCT91_CH_CURR_PTR	0x402896CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT91_INTR	0x402896D0	FULL	Interrupt
DW0_CH_STRUCT91_INTR_SET	0x402896D4	FULL	Interrupt set
DW0_CH_STRUCT91_INTR_MASK	0x402896D8	FULL	Interrupt mask
DW0_CH_STRUCT91_INTR_MASKED	0x402896DC	FULL	Interrupt masked
DW0_CH_STRUCT91_SRAM_DATA0	0x402896E0	FULL	SRAM data 0
DW0_CH_STRUCT91_SRAM_DATA1	0x402896E4	FULL	SRAM data 1
DW0_CH_STRUCT91_TR_CMD	0x402896E8	FULL	Channel software trigger

8.1.1.93 CH_STRUCT 92

Register Name	Address	Permission	Description
DW0_CH_STRUCT92_CH_CTL	0x40289700	FULL	Channel control
DW0_CH_STRUCT92_CH_STATUS	0x40289704	FULL	Channel status
DW0_CH_STRUCT92_CH_IDX	0x40289708	FULL	Channel current indices

Register Name	Address	Permission	Description
DW0_CH_STRUCT92_CH_CURR_PTR	0x4028970C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT92_INTR	0x40289710	FULL	Interrupt
DW0_CH_STRUCT92_INTR_SET	0x40289714	FULL	Interrupt set
DW0_CH_STRUCT92_INTR_MASK	0x40289718	FULL	Interrupt mask
DW0_CH_STRUCT92_INTR_MASKED	0x4028971C	FULL	Interrupt masked
DW0_CH_STRUCT92_SRAM_DATA0	0x40289720	FULL	SRAM data 0
DW0_CH_STRUCT92_SRAM_DATA1	0x40289724	FULL	SRAM data 1
DW0_CH_STRUCT92_TR_CMD	0x40289728	FULL	Channel software trigger

8.1.1.94 CH_STRUCT 93

Register Name	Address	Permission	Description
DW0_CH_STRUCT93_CH_CTL	0x40289740	FULL	Channel control
DW0_CH_STRUCT93_CH_STATUS	0x40289744	FULL	Channel status
DW0_CH_STRUCT93_CH_IDX	0x40289748	FULL	Channel current indices
DW0_CH_STRUCT93_CH_CURR_PTR	0x4028974C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT93_INTR	0x40289750	FULL	Interrupt
DW0_CH_STRUCT93_INTR_SET	0x40289754	FULL	Interrupt set
DW0_CH_STRUCT93_INTR_MASK	0x40289758	FULL	Interrupt mask
DW0_CH_STRUCT93_INTR_MASKED	0x4028975C	FULL	Interrupt masked
DW0_CH_STRUCT93_SRAM_DATA0	0x40289760	FULL	SRAM data 0
DW0_CH_STRUCT93_SRAM_DATA1	0x40289764	FULL	SRAM data 1
DW0_CH_STRUCT93_TR_CMD	0x40289768	FULL	Channel software trigger

8.1.1.95 CH_STRUCT 94

Register Name	Address	Permission	Description
DW0_CH_STRUCT94_CH_CTL	0x40289780	FULL	Channel control
DW0_CH_STRUCT94_CH_STATUS	0x40289784	FULL	Channel status
DW0_CH_STRUCT94_CH_IDX	0x40289788	FULL	Channel current indices
DW0_CH_STRUCT94_CH_CURR_PTR	0x4028978C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT94_INTR	0x40289790	FULL	Interrupt
DW0_CH_STRUCT94_INTR_SET	0x40289794	FULL	Interrupt set
DW0_CH_STRUCT94_INTR_MASK	0x40289798	FULL	Interrupt mask
DW0_CH_STRUCT94_INTR_MASKED	0x4028979C	FULL	Interrupt masked
DW0_CH_STRUCT94_SRAM_DATA0	0x402897A0	FULL	SRAM data 0
DW0_CH_STRUCT94_SRAM_DATA1	0x402897A4	FULL	SRAM data 1
DW0_CH_STRUCT94_TR_CMD	0x402897A8	FULL	Channel software trigger

8.1.1.96 CH_STRUCT 95

Register Name	Address	Permission	Description
DW0_CH_STRUCT95_CH_CTL	0x402897C0	FULL	Channel control
DW0_CH_STRUCT95_CH_STATUS	0x402897C4	FULL	Channel status
DW0_CH_STRUCT95_CH_IDX	0x402897C8	FULL	Channel current indices
DW0_CH_STRUCT95_CH_CURR_PTR	0x402897CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT95_INTR	0x402897D0	FULL	Interrupt
DW0_CH_STRUCT95_INTR_SET	0x402897D4	FULL	Interrupt set
DW0_CH_STRUCT95_INTR_MASK	0x402897D8	FULL	Interrupt mask
DW0_CH_STRUCT95_INTR_MASKED	0x402897DC	FULL	Interrupt masked
DW0_CH_STRUCT95_SRAM_DATA0	0x402897E0	FULL	SRAM data 0
DW0_CH_STRUCT95_SRAM_DATA1	0x402897E4	FULL	SRAM data 1
DW0_CH_STRUCT95_TR_CMD	0x402897E8	FULL	Channel software trigger

8.1.1.97 CH_STRUCT 96

Register Name	Address	Permission	Description
DW0_CH_STRUCT96_CH_CTL	0x40289800	FULL	Channel control
DW0_CH_STRUCT96_CH_STATUS	0x40289804	FULL	Channel status
DW0_CH_STRUCT96_CH_IDX	0x40289808	FULL	Channel current indices
DW0_CH_STRUCT96_CH_CURR_PTR	0x4028980C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT96_INTR	0x40289810	FULL	Interrupt
DW0_CH_STRUCT96_INTR_SET	0x40289814	FULL	Interrupt set
DW0_CH_STRUCT96_INTR_MASK	0x40289818	FULL	Interrupt mask
DW0_CH_STRUCT96_INTR_MASKED	0x4028981C	FULL	Interrupt masked
DW0_CH_STRUCT96_SRAM_DATA0	0x40289820	FULL	SRAM data 0
DW0_CH_STRUCT96_SRAM_DATA1	0x40289824	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW0_CH_STRUCT96_TR_CMD	0x40289828	FULL	Channel software trigger

8.1.1.98 CH_STRUCT 97

Register Name	Address	Permission	Description
DW0_CH_STRUCT97_CH_CTL	0x40289840	FULL	Channel control
DW0_CH_STRUCT97_CH_STATUS	0x40289844	FULL	Channel status
DW0_CH_STRUCT97_CH_IDX	0x40289848	FULL	Channel current indices
DW0_CH_STRUCT97_CH_CURR_PTR	0x4028984C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT97_INTR	0x40289850	FULL	Interrupt
DW0_CH_STRUCT97_INTR_SET	0x40289854	FULL	Interrupt set
DW0_CH_STRUCT97_INTR_MASK	0x40289858	FULL	Interrupt mask
DW0_CH_STRUCT97_INTR_MASKED	0x4028985C	FULL	Interrupt masked
DW0_CH_STRUCT97_SRAM_DATA0	0x40289860	FULL	SRAM data 0
DW0_CH_STRUCT97_SRAM_DATA1	0x40289864	FULL	SRAM data 1
DW0_CH_STRUCT97_TR_CMD	0x40289868	FULL	Channel software trigger

8.1.1.99 CH_STRUCT 98

Register Name	Address	Permission	Description
DW0_CH_STRUCT98_CH_CTL	0x40289880	FULL	Channel control
DW0_CH_STRUCT98_CH_STATUS	0x40289884	FULL	Channel status
DW0_CH_STRUCT98_CH_IDX	0x40289888	FULL	Channel current indices
DW0_CH_STRUCT98_CH_CURR_PTR	0x4028988C	FULL	Channel current descriptor pointer
DW0_CH_STRUCT98_INTR	0x40289890	FULL	Interrupt
DW0_CH_STRUCT98_INTR_SET	0x40289894	FULL	Interrupt set
DW0_CH_STRUCT98_INTR_MASK	0x40289898	FULL	Interrupt mask
DW0_CH_STRUCT98_INTR_MASKED	0x4028989C	FULL	Interrupt masked
DW0_CH_STRUCT98_SRAM_DATA0	0x402898A0	FULL	SRAM data 0
DW0_CH_STRUCT98_SRAM_DATA1	0x402898A4	FULL	SRAM data 1
DW0_CH_STRUCT98_TR_CMD	0x402898A8	FULL	Channel software trigger

8.1.1.100 CH_STRUCT 99

Register Name	Address	Permission	Description
DW0_CH_STRUCT99_CH_CTL	0x402898C0	FULL	Channel control
DW0_CH_STRUCT99_CH_STATUS	0x402898C4	FULL	Channel status
DW0_CH_STRUCT99_CH_IDX	0x402898C8	FULL	Channel current indices
DW0_CH_STRUCT99_CH_CURR_PTR	0x402898CC	FULL	Channel current descriptor pointer
DW0_CH_STRUCT99_INTR	0x402898D0	FULL	Interrupt
DW0_CH_STRUCT99_INTR_SET	0x402898D4	FULL	Interrupt set
DW0_CH_STRUCT99_INTR_MASK	0x402898D8	FULL	Interrupt mask
DW0_CH_STRUCT99_INTR_MASKED	0x402898DC	FULL	Interrupt masked
DW0_CH_STRUCT99_SRAM_DATA0	0x402898E0	FULL	SRAM data 0
DW0_CH_STRUCT99_SRAM_DATA1	0x402898E4	FULL	SRAM data 1
DW0_CH_STRUCT99_TR_CMD	0x402898E8	FULL	Channel software trigger

8.2 DW 1

Description	Datawire Controller
Base Address	0x40290000
Size	0x10000
Slave Num	MMIO2 - 8

8.2.1 0

Register Name	Address	Permission	Description
DW1_CTL0	0x40290000	FULL	Control
DW1_STATUS0	0x40290004	FULL	Status
DW1_ACT_DESCR_CTL0	0x40290020	FULL	Active descriptor control
DW1_ACT_DESCR_SRC0	0x40290024	FULL	Active descriptor source
DW1_ACT_DESCR_DST0	0x40290028	FULL	Active descriptor destination
DW1_ACT_DESCR_X_CTL0	0x40290030	FULL	Active descriptor X loop control
DW1_ACT_DESCR_Y_CTL0	0x40290034	FULL	Active descriptor Y loop control
DW1_ACT_DESCR_NEXT_PTR0	0x40290038	FULL	Active descriptor next pointer
DW1_ACT_SRC0	0x40290040	FULL	Active source

Register Name	Address	Permission	Description
DW1_ACT_DST0	0x40290044	FULL	Active destination
DW1_ECC_CTL0	0x40290080	FULL	ECC control
DW1_CRC_CTL0	0x40290100	FULL	CRC control
DW1_CRC_DATA_CTL0	0x40290110	FULL	CRC data control
DW1_CRC_POL_CTL0	0x40290120	FULL	CRC polynomial control
DW1_CRC_LFSR_CTL0	0x40290130	FULL	CRC LFSR control
DW1_CRC_REM_CTL0	0x40290140	FULL	CRC remainder control
DW1_CRC_REM_RESULT0	0x40290148	FULL	CRC remainder result

8.2.1.1 CH_STRUCT 0

Register Name	Address	Permission	Description
DW1_CH_STRUCT0_CH_CTL	0x40298000	FULL	Channel control
DW1_CH_STRUCT0_CH_STATUS	0x40298004	FULL	Channel status
DW1_CH_STRUCT0_CH_IDX	0x40298008	FULL	Channel current indices
DW1_CH_STRUCT0_CH_CURR_PTR	0x4029800C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT0_INTR	0x40298010	FULL	Interrupt
DW1_CH_STRUCT0_INTR_SET	0x40298014	FULL	Interrupt set
DW1_CH_STRUCT0_INTR_MASK	0x40298018	FULL	Interrupt mask
DW1_CH_STRUCT0_INTR_MASKED	0x4029801C	FULL	Interrupt masked
DW1_CH_STRUCT0_SRAM_DATA0	0x40298020	FULL	SRAM data 0
DW1_CH_STRUCT0_SRAM_DATA1	0x40298024	FULL	SRAM data 1
DW1_CH_STRUCT0_TR_CMD	0x40298028	FULL	Channel software trigger

8.2.1.2 CH_STRUCT 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT1_CH_CTL	0x40298040	FULL	Channel control
DW1_CH_STRUCT1_CH_STATUS	0x40298044	FULL	Channel status
DW1_CH_STRUCT1_CH_IDX	0x40298048	FULL	Channel current indices
DW1_CH_STRUCT1_CH_CURR_PTR	0x4029804C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT1_INTR	0x40298050	FULL	Interrupt
DW1_CH_STRUCT1_INTR_SET	0x40298054	FULL	Interrupt set
DW1_CH_STRUCT1_INTR_MASK	0x40298058	FULL	Interrupt mask
DW1_CH_STRUCT1_INTR_MASKED	0x4029805C	FULL	Interrupt masked
DW1_CH_STRUCT1_SRAM_DATA0	0x40298060	FULL	SRAM data 0
DW1_CH_STRUCT1_SRAM_DATA1	0x40298064	FULL	SRAM data 1
DW1_CH_STRUCT1_TR_CMD	0x40298068	FULL	Channel software trigger

8.2.1.3 CH_STRUCT 2

Register Name	Address	Permission	Description
DW1_CH_STRUCT2_CH_CTL	0x40298080	FULL	Channel control
DW1_CH_STRUCT2_CH_STATUS	0x40298084	FULL	Channel status
DW1_CH_STRUCT2_CH_IDX	0x40298088	FULL	Channel current indices
DW1_CH_STRUCT2_CH_CURR_PTR	0x4029808C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT2_INTR	0x40298090	FULL	Interrupt
DW1_CH_STRUCT2_INTR_SET	0x40298094	FULL	Interrupt set
DW1_CH_STRUCT2_INTR_MASK	0x40298098	FULL	Interrupt mask
DW1_CH_STRUCT2_INTR_MASKED	0x4029809C	FULL	Interrupt masked
DW1_CH_STRUCT2_SRAM_DATA0	0x402980A0	FULL	SRAM data 0
DW1_CH_STRUCT2_SRAM_DATA1	0x402980A4	FULL	SRAM data 1
DW1_CH_STRUCT2_TR_CMD	0x402980A8	FULL	Channel software trigger

8.2.1.4 CH_STRUCT 3

Register Name	Address	Permission	Description
DW1_CH_STRUCT3_CH_CTL	0x402980C0	FULL	Channel control
DW1_CH_STRUCT3_CH_STATUS	0x402980C4	FULL	Channel status
DW1_CH_STRUCT3_CH_IDX	0x402980C8	FULL	Channel current indices
DW1_CH_STRUCT3_CH_CURR_PTR	0x402980CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT3_INTR	0x402980D0	FULL	Interrupt
DW1_CH_STRUCT3_INTR_SET	0x402980D4	FULL	Interrupt set
DW1_CH_STRUCT3_INTR_MASK	0x402980D8	FULL	Interrupt mask
DW1_CH_STRUCT3_INTR_MASKED	0x402980DC	FULL	Interrupt masked
DW1_CH_STRUCT3_SRAM_DATA0	0x402980E0	FULL	SRAM data 0
DW1_CH_STRUCT3_SRAM_DATA1	0x402980E4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT3_TR_CMD	0x402980E8	FULL	Channel software trigger

8.2.1.5 CH_STRUCT 4

Register Name	Address	Permission	Description
DW1_CH_STRUCT4_CH_CTL	0x40298100	FULL	Channel control
DW1_CH_STRUCT4_CH_STATUS	0x40298104	FULL	Channel status
DW1_CH_STRUCT4_CH_IDX	0x40298108	FULL	Channel current indices
DW1_CH_STRUCT4_CH_CURR_PTR	0x4029810C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT4_INTR	0x40298110	FULL	Interrupt
DW1_CH_STRUCT4_INTR_SET	0x40298114	FULL	Interrupt set
DW1_CH_STRUCT4_INTR_MASK	0x40298118	FULL	Interrupt mask
DW1_CH_STRUCT4_INTR_MASKED	0x4029811C	FULL	Interrupt masked
DW1_CH_STRUCT4_SRAM_DATA0	0x40298120	FULL	SRAM data 0
DW1_CH_STRUCT4_SRAM_DATA1	0x40298124	FULL	SRAM data 1
DW1_CH_STRUCT4_TR_CMD	0x40298128	FULL	Channel software trigger

8.2.1.6 CH_STRUCT 5

Register Name	Address	Permission	Description
DW1_CH_STRUCT5_CH_CTL	0x40298140	FULL	Channel control
DW1_CH_STRUCT5_CH_STATUS	0x40298144	FULL	Channel status
DW1_CH_STRUCT5_CH_IDX	0x40298148	FULL	Channel current indices
DW1_CH_STRUCT5_CH_CURR_PTR	0x4029814C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT5_INTR	0x40298150	FULL	Interrupt
DW1_CH_STRUCT5_INTR_SET	0x40298154	FULL	Interrupt set
DW1_CH_STRUCT5_INTR_MASK	0x40298158	FULL	Interrupt mask
DW1_CH_STRUCT5_INTR_MASKED	0x4029815C	FULL	Interrupt masked
DW1_CH_STRUCT5_SRAM_DATA0	0x40298160	FULL	SRAM data 0
DW1_CH_STRUCT5_SRAM_DATA1	0x40298164	FULL	SRAM data 1
DW1_CH_STRUCT5_TR_CMD	0x40298168	FULL	Channel software trigger

8.2.1.7 CH_STRUCT 6

Register Name	Address	Permission	Description
DW1_CH_STRUCT6_CH_CTL	0x40298180	FULL	Channel control
DW1_CH_STRUCT6_CH_STATUS	0x40298184	FULL	Channel status
DW1_CH_STRUCT6_CH_IDX	0x40298188	FULL	Channel current indices
DW1_CH_STRUCT6_CH_CURR_PTR	0x4029818C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT6_INTR	0x40298190	FULL	Interrupt
DW1_CH_STRUCT6_INTR_SET	0x40298194	FULL	Interrupt set
DW1_CH_STRUCT6_INTR_MASK	0x40298198	FULL	Interrupt mask
DW1_CH_STRUCT6_INTR_MASKED	0x4029819C	FULL	Interrupt masked
DW1_CH_STRUCT6_SRAM_DATA0	0x402981A0	FULL	SRAM data 0
DW1_CH_STRUCT6_SRAM_DATA1	0x402981A4	FULL	SRAM data 1
DW1_CH_STRUCT6_TR_CMD	0x402981A8	FULL	Channel software trigger

8.2.1.8 CH_STRUCT 7

Register Name	Address	Permission	Description
DW1_CH_STRUCT7_CH_CTL	0x402981C0	FULL	Channel control
DW1_CH_STRUCT7_CH_STATUS	0x402981C4	FULL	Channel status
DW1_CH_STRUCT7_CH_IDX	0x402981C8	FULL	Channel current indices
DW1_CH_STRUCT7_CH_CURR_PTR	0x402981CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT7_INTR	0x402981D0	FULL	Interrupt
DW1_CH_STRUCT7_INTR_SET	0x402981D4	FULL	Interrupt set
DW1_CH_STRUCT7_INTR_MASK	0x402981D8	FULL	Interrupt mask
DW1_CH_STRUCT7_INTR_MASKED	0x402981DC	FULL	Interrupt masked
DW1_CH_STRUCT7_SRAM_DATA0	0x402981E0	FULL	SRAM data 0
DW1_CH_STRUCT7_SRAM_DATA1	0x402981E4	FULL	SRAM data 1
DW1_CH_STRUCT7_TR_CMD	0x402981E8	FULL	Channel software trigger

8.2.1.9 CH_STRUCT 8

Register Name	Address	Permission	Description
DW1_CH_STRUCT8_CH_CTL	0x40298200	FULL	Channel control
DW1_CH_STRUCT8_CH_STATUS	0x40298204	FULL	Channel status
DW1_CH_STRUCT8_CH_IDX	0x40298208	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT8_CH_CURR_PTR	0x4029820C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT8_INTR	0x40298210	FULL	Interrupt
DW1_CH_STRUCT8_INTR_SET	0x40298214	FULL	Interrupt set
DW1_CH_STRUCT8_INTR_MASK	0x40298218	FULL	Interrupt mask
DW1_CH_STRUCT8_INTR_MASKED	0x4029821C	FULL	Interrupt masked
DW1_CH_STRUCT8_SRAM_DATA0	0x40298220	FULL	SRAM data 0
DW1_CH_STRUCT8_SRAM_DATA1	0x40298224	FULL	SRAM data 1
DW1_CH_STRUCT8_TR_CMD	0x40298228	FULL	Channel software trigger

8.2.1.10 CH_STRUCT 9

Register Name	Address	Permission	Description
DW1_CH_STRUCT9_CH_CTL	0x40298240	FULL	Channel control
DW1_CH_STRUCT9_CH_STATUS	0x40298244	FULL	Channel status
DW1_CH_STRUCT9_CH_IDX	0x40298248	FULL	Channel current indices
DW1_CH_STRUCT9_CH_CURR_PTR	0x4029824C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT9_INTR	0x40298250	FULL	Interrupt
DW1_CH_STRUCT9_INTR_SET	0x40298254	FULL	Interrupt set
DW1_CH_STRUCT9_INTR_MASK	0x40298258	FULL	Interrupt mask
DW1_CH_STRUCT9_INTR_MASKED	0x4029825C	FULL	Interrupt masked
DW1_CH_STRUCT9_SRAM_DATA0	0x40298260	FULL	SRAM data 0
DW1_CH_STRUCT9_SRAM_DATA1	0x40298264	FULL	SRAM data 1
DW1_CH_STRUCT9_TR_CMD	0x40298268	FULL	Channel software trigger

8.2.1.11 CH_STRUCT 10

Register Name	Address	Permission	Description
DW1_CH_STRUCT10_CH_CTL	0x40298280	FULL	Channel control
DW1_CH_STRUCT10_CH_STATUS	0x40298284	FULL	Channel status
DW1_CH_STRUCT10_CH_IDX	0x40298288	FULL	Channel current indices
DW1_CH_STRUCT10_CH_CURR_PTR	0x4029828C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT10_INTR	0x40298290	FULL	Interrupt
DW1_CH_STRUCT10_INTR_SET	0x40298294	FULL	Interrupt set
DW1_CH_STRUCT10_INTR_MASK	0x40298298	FULL	Interrupt mask
DW1_CH_STRUCT10_INTR_MASKED	0x4029829C	FULL	Interrupt masked
DW1_CH_STRUCT10_SRAM_DATA0	0x402982A0	FULL	SRAM data 0
DW1_CH_STRUCT10_SRAM_DATA1	0x402982A4	FULL	SRAM data 1
DW1_CH_STRUCT10_TR_CMD	0x402982A8	FULL	Channel software trigger

8.2.1.12 CH_STRUCT 11

Register Name	Address	Permission	Description
DW1_CH_STRUCT11_CH_CTL	0x402982C0	FULL	Channel control
DW1_CH_STRUCT11_CH_STATUS	0x402982C4	FULL	Channel status
DW1_CH_STRUCT11_CH_IDX	0x402982C8	FULL	Channel current indices
DW1_CH_STRUCT11_CH_CURR_PTR	0x402982CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT11_INTR	0x402982D0	FULL	Interrupt
DW1_CH_STRUCT11_INTR_SET	0x402982D4	FULL	Interrupt set
DW1_CH_STRUCT11_INTR_MASK	0x402982D8	FULL	Interrupt mask
DW1_CH_STRUCT11_INTR_MASKED	0x402982DC	FULL	Interrupt masked
DW1_CH_STRUCT11_SRAM_DATA0	0x402982E0	FULL	SRAM data 0
DW1_CH_STRUCT11_SRAM_DATA1	0x402982E4	FULL	SRAM data 1
DW1_CH_STRUCT11_TR_CMD	0x402982E8	FULL	Channel software trigger

8.2.1.13 CH_STRUCT 12

Register Name	Address	Permission	Description
DW1_CH_STRUCT12_CH_CTL	0x40298300	FULL	Channel control
DW1_CH_STRUCT12_CH_STATUS	0x40298304	FULL	Channel status
DW1_CH_STRUCT12_CH_IDX	0x40298308	FULL	Channel current indices
DW1_CH_STRUCT12_CH_CURR_PTR	0x4029830C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT12_INTR	0x40298310	FULL	Interrupt
DW1_CH_STRUCT12_INTR_SET	0x40298314	FULL	Interrupt set
DW1_CH_STRUCT12_INTR_MASK	0x40298318	FULL	Interrupt mask
DW1_CH_STRUCT12_INTR_MASKED	0x4029831C	FULL	Interrupt masked
DW1_CH_STRUCT12_SRAM_DATA0	0x40298320	FULL	SRAM data 0
DW1_CH_STRUCT12_SRAM_DATA1	0x40298324	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT12_TR_CMD	0x40298328	FULL	Channel software trigger

8.2.1.14 CH_STRUCT 13

Register Name	Address	Permission	Description
DW1_CH_STRUCT13_CH_CTL	0x40298340	FULL	Channel control
DW1_CH_STRUCT13_CH_STATUS	0x40298344	FULL	Channel status
DW1_CH_STRUCT13_CH_IDX	0x40298348	FULL	Channel current indices
DW1_CH_STRUCT13_CH_CURR_PTR	0x4029834C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT13_INTR	0x40298350	FULL	Interrupt
DW1_CH_STRUCT13_INTR_SET	0x40298354	FULL	Interrupt set
DW1_CH_STRUCT13_INTR_MASK	0x40298358	FULL	Interrupt mask
DW1_CH_STRUCT13_INTR_MASKED	0x4029835C	FULL	Interrupt masked
DW1_CH_STRUCT13_SRAM_DATA0	0x40298360	FULL	SRAM data 0
DW1_CH_STRUCT13_SRAM_DATA1	0x40298364	FULL	SRAM data 1
DW1_CH_STRUCT13_TR_CMD	0x40298368	FULL	Channel software trigger

8.2.1.15 CH_STRUCT 14

Register Name	Address	Permission	Description
DW1_CH_STRUCT14_CH_CTL	0x40298380	FULL	Channel control
DW1_CH_STRUCT14_CH_STATUS	0x40298384	FULL	Channel status
DW1_CH_STRUCT14_CH_IDX	0x40298388	FULL	Channel current indices
DW1_CH_STRUCT14_CH_CURR_PTR	0x4029838C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT14_INTR	0x40298390	FULL	Interrupt
DW1_CH_STRUCT14_INTR_SET	0x40298394	FULL	Interrupt set
DW1_CH_STRUCT14_INTR_MASK	0x40298398	FULL	Interrupt mask
DW1_CH_STRUCT14_INTR_MASKED	0x4029839C	FULL	Interrupt masked
DW1_CH_STRUCT14_SRAM_DATA0	0x402983A0	FULL	SRAM data 0
DW1_CH_STRUCT14_SRAM_DATA1	0x402983A4	FULL	SRAM data 1
DW1_CH_STRUCT14_TR_CMD	0x402983A8	FULL	Channel software trigger

8.2.1.16 CH_STRUCT 15

Register Name	Address	Permission	Description
DW1_CH_STRUCT15_CH_CTL	0x402983C0	FULL	Channel control
DW1_CH_STRUCT15_CH_STATUS	0x402983C4	FULL	Channel status
DW1_CH_STRUCT15_CH_IDX	0x402983C8	FULL	Channel current indices
DW1_CH_STRUCT15_CH_CURR_PTR	0x402983CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT15_INTR	0x402983D0	FULL	Interrupt
DW1_CH_STRUCT15_INTR_SET	0x402983D4	FULL	Interrupt set
DW1_CH_STRUCT15_INTR_MASK	0x402983D8	FULL	Interrupt mask
DW1_CH_STRUCT15_INTR_MASKED	0x402983DC	FULL	Interrupt masked
DW1_CH_STRUCT15_SRAM_DATA0	0x402983E0	FULL	SRAM data 0
DW1_CH_STRUCT15_SRAM_DATA1	0x402983E4	FULL	SRAM data 1
DW1_CH_STRUCT15_TR_CMD	0x402983E8	FULL	Channel software trigger

8.2.1.17 CH_STRUCT 16

Register Name	Address	Permission	Description
DW1_CH_STRUCT16_CH_CTL	0x40298400	FULL	Channel control
DW1_CH_STRUCT16_CH_STATUS	0x40298404	FULL	Channel status
DW1_CH_STRUCT16_CH_IDX	0x40298408	FULL	Channel current indices
DW1_CH_STRUCT16_CH_CURR_PTR	0x4029840C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT16_INTR	0x40298410	FULL	Interrupt
DW1_CH_STRUCT16_INTR_SET	0x40298414	FULL	Interrupt set
DW1_CH_STRUCT16_INTR_MASK	0x40298418	FULL	Interrupt mask
DW1_CH_STRUCT16_INTR_MASKED	0x4029841C	FULL	Interrupt masked
DW1_CH_STRUCT16_SRAM_DATA0	0x40298420	FULL	SRAM data 0
DW1_CH_STRUCT16_SRAM_DATA1	0x40298424	FULL	SRAM data 1
DW1_CH_STRUCT16_TR_CMD	0x40298428	FULL	Channel software trigger

8.2.1.18 CH_STRUCT 17

Register Name	Address	Permission	Description
DW1_CH_STRUCT17_CH_CTL	0x40298440	FULL	Channel control
DW1_CH_STRUCT17_CH_STATUS	0x40298444	FULL	Channel status
DW1_CH_STRUCT17_CH_IDX	0x40298448	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT17_CH_CURR_PTR	0x4029844C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT17_INTR	0x40298450	FULL	Interrupt
DW1_CH_STRUCT17_INTR_SET	0x40298454	FULL	Interrupt set
DW1_CH_STRUCT17_INTR_MASK	0x40298458	FULL	Interrupt mask
DW1_CH_STRUCT17_INTR_MASKED	0x4029845C	FULL	Interrupt masked
DW1_CH_STRUCT17_SRAM_DATA0	0x40298460	FULL	SRAM data 0
DW1_CH_STRUCT17_SRAM_DATA1	0x40298464	FULL	SRAM data 1
DW1_CH_STRUCT17_TR_CMD	0x40298468	FULL	Channel software trigger

8.2.1.19 CH_STRUCT 18

Register Name	Address	Permission	Description
DW1_CH_STRUCT18_CH_CTL	0x40298480	FULL	Channel control
DW1_CH_STRUCT18_CH_STATUS	0x40298484	FULL	Channel status
DW1_CH_STRUCT18_CH_IDX	0x40298488	FULL	Channel current indices
DW1_CH_STRUCT18_CH_CURR_PTR	0x4029848C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT18_INTR	0x40298490	FULL	Interrupt
DW1_CH_STRUCT18_INTR_SET	0x40298494	FULL	Interrupt set
DW1_CH_STRUCT18_INTR_MASK	0x40298498	FULL	Interrupt mask
DW1_CH_STRUCT18_INTR_MASKED	0x4029849C	FULL	Interrupt masked
DW1_CH_STRUCT18_SRAM_DATA0	0x402984A0	FULL	SRAM data 0
DW1_CH_STRUCT18_SRAM_DATA1	0x402984A4	FULL	SRAM data 1
DW1_CH_STRUCT18_TR_CMD	0x402984A8	FULL	Channel software trigger

8.2.1.20 CH_STRUCT 19

Register Name	Address	Permission	Description
DW1_CH_STRUCT19_CH_CTL	0x402984C0	FULL	Channel control
DW1_CH_STRUCT19_CH_STATUS	0x402984C4	FULL	Channel status
DW1_CH_STRUCT19_CH_IDX	0x402984C8	FULL	Channel current indices
DW1_CH_STRUCT19_CH_CURR_PTR	0x402984CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT19_INTR	0x402984D0	FULL	Interrupt
DW1_CH_STRUCT19_INTR_SET	0x402984D4	FULL	Interrupt set
DW1_CH_STRUCT19_INTR_MASK	0x402984D8	FULL	Interrupt mask
DW1_CH_STRUCT19_INTR_MASKED	0x402984DC	FULL	Interrupt masked
DW1_CH_STRUCT19_SRAM_DATA0	0x402984E0	FULL	SRAM data 0
DW1_CH_STRUCT19_SRAM_DATA1	0x402984E4	FULL	SRAM data 1
DW1_CH_STRUCT19_TR_CMD	0x402984E8	FULL	Channel software trigger

8.2.1.21 CH_STRUCT 20

Register Name	Address	Permission	Description
DW1_CH_STRUCT20_CH_CTL	0x40298500	FULL	Channel control
DW1_CH_STRUCT20_CH_STATUS	0x40298504	FULL	Channel status
DW1_CH_STRUCT20_CH_IDX	0x40298508	FULL	Channel current indices
DW1_CH_STRUCT20_CH_CURR_PTR	0x4029850C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT20_INTR	0x40298510	FULL	Interrupt
DW1_CH_STRUCT20_INTR_SET	0x40298514	FULL	Interrupt set
DW1_CH_STRUCT20_INTR_MASK	0x40298518	FULL	Interrupt mask
DW1_CH_STRUCT20_INTR_MASKED	0x4029851C	FULL	Interrupt masked
DW1_CH_STRUCT20_SRAM_DATA0	0x40298520	FULL	SRAM data 0
DW1_CH_STRUCT20_SRAM_DATA1	0x40298524	FULL	SRAM data 1
DW1_CH_STRUCT20_TR_CMD	0x40298528	FULL	Channel software trigger

8.2.1.22 CH_STRUCT 21

Register Name	Address	Permission	Description
DW1_CH_STRUCT21_CH_CTL	0x40298540	FULL	Channel control
DW1_CH_STRUCT21_CH_STATUS	0x40298544	FULL	Channel status
DW1_CH_STRUCT21_CH_IDX	0x40298548	FULL	Channel current indices
DW1_CH_STRUCT21_CH_CURR_PTR	0x4029854C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT21_INTR	0x40298550	FULL	Interrupt
DW1_CH_STRUCT21_INTR_SET	0x40298554	FULL	Interrupt set
DW1_CH_STRUCT21_INTR_MASK	0x40298558	FULL	Interrupt mask
DW1_CH_STRUCT21_INTR_MASKED	0x4029855C	FULL	Interrupt masked
DW1_CH_STRUCT21_SRAM_DATA0	0x40298560	FULL	SRAM data 0
DW1_CH_STRUCT21_SRAM_DATA1	0x40298564	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT21_TR_CMD	0x40298568	FULL	Channel software trigger

8.2.1.23 CH_STRUCT 22

Register Name	Address	Permission	Description
DW1_CH_STRUCT22_CH_CTL	0x40298580	FULL	Channel control
DW1_CH_STRUCT22_CH_STATUS	0x40298584	FULL	Channel status
DW1_CH_STRUCT22_CH_IDX	0x40298588	FULL	Channel current indices
DW1_CH_STRUCT22_CH_CURR_PTR	0x4029858C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT22_INTR	0x40298590	FULL	Interrupt
DW1_CH_STRUCT22_INTR_SET	0x40298594	FULL	Interrupt set
DW1_CH_STRUCT22_INTR_MASK	0x40298598	FULL	Interrupt mask
DW1_CH_STRUCT22_INTR_MASKED	0x4029859C	FULL	Interrupt masked
DW1_CH_STRUCT22_SRAM_DATA0	0x402985A0	FULL	SRAM data 0
DW1_CH_STRUCT22_SRAM_DATA1	0x402985A4	FULL	SRAM data 1
DW1_CH_STRUCT22_TR_CMD	0x402985A8	FULL	Channel software trigger

8.2.1.24 CH_STRUCT 23

Register Name	Address	Permission	Description
DW1_CH_STRUCT23_CH_CTL	0x402985C0	FULL	Channel control
DW1_CH_STRUCT23_CH_STATUS	0x402985C4	FULL	Channel status
DW1_CH_STRUCT23_CH_IDX	0x402985C8	FULL	Channel current indices
DW1_CH_STRUCT23_CH_CURR_PTR	0x402985CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT23_INTR	0x402985D0	FULL	Interrupt
DW1_CH_STRUCT23_INTR_SET	0x402985D4	FULL	Interrupt set
DW1_CH_STRUCT23_INTR_MASK	0x402985D8	FULL	Interrupt mask
DW1_CH_STRUCT23_INTR_MASKED	0x402985DC	FULL	Interrupt masked
DW1_CH_STRUCT23_SRAM_DATA0	0x402985E0	FULL	SRAM data 0
DW1_CH_STRUCT23_SRAM_DATA1	0x402985E4	FULL	SRAM data 1
DW1_CH_STRUCT23_TR_CMD	0x402985E8	FULL	Channel software trigger

8.2.1.25 CH_STRUCT 24

Register Name	Address	Permission	Description
DW1_CH_STRUCT24_CH_CTL	0x40298600	FULL	Channel control
DW1_CH_STRUCT24_CH_STATUS	0x40298604	FULL	Channel status
DW1_CH_STRUCT24_CH_IDX	0x40298608	FULL	Channel current indices
DW1_CH_STRUCT24_CH_CURR_PTR	0x4029860C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT24_INTR	0x40298610	FULL	Interrupt
DW1_CH_STRUCT24_INTR_SET	0x40298614	FULL	Interrupt set
DW1_CH_STRUCT24_INTR_MASK	0x40298618	FULL	Interrupt mask
DW1_CH_STRUCT24_INTR_MASKED	0x4029861C	FULL	Interrupt masked
DW1_CH_STRUCT24_SRAM_DATA0	0x40298620	FULL	SRAM data 0
DW1_CH_STRUCT24_SRAM_DATA1	0x40298624	FULL	SRAM data 1
DW1_CH_STRUCT24_TR_CMD	0x40298628	FULL	Channel software trigger

8.2.1.26 CH_STRUCT 25

Register Name	Address	Permission	Description
DW1_CH_STRUCT25_CH_CTL	0x40298640	FULL	Channel control
DW1_CH_STRUCT25_CH_STATUS	0x40298644	FULL	Channel status
DW1_CH_STRUCT25_CH_IDX	0x40298648	FULL	Channel current indices
DW1_CH_STRUCT25_CH_CURR_PTR	0x4029864C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT25_INTR	0x40298650	FULL	Interrupt
DW1_CH_STRUCT25_INTR_SET	0x40298654	FULL	Interrupt set
DW1_CH_STRUCT25_INTR_MASK	0x40298658	FULL	Interrupt mask
DW1_CH_STRUCT25_INTR_MASKED	0x4029865C	FULL	Interrupt masked
DW1_CH_STRUCT25_SRAM_DATA0	0x40298660	FULL	SRAM data 0
DW1_CH_STRUCT25_SRAM_DATA1	0x40298664	FULL	SRAM data 1
DW1_CH_STRUCT25_TR_CMD	0x40298668	FULL	Channel software trigger

8.2.1.27 CH_STRUCT 26

Register Name	Address	Permission	Description
DW1_CH_STRUCT26_CH_CTL	0x40298680	FULL	Channel control
DW1_CH_STRUCT26_CH_STATUS	0x40298684	FULL	Channel status
DW1_CH_STRUCT26_CH_IDX	0x40298688	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT26_CH_CURR_PTR	0x4029868C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT26_INTR	0x40298690	FULL	Interrupt
DW1_CH_STRUCT26_INTR_SET	0x40298694	FULL	Interrupt set
DW1_CH_STRUCT26_INTR_MASK	0x40298698	FULL	Interrupt mask
DW1_CH_STRUCT26_INTR_MASKED	0x4029869C	FULL	Interrupt masked
DW1_CH_STRUCT26_SRAM_DATA0	0x402986A0	FULL	SRAM data 0
DW1_CH_STRUCT26_SRAM_DATA1	0x402986A4	FULL	SRAM data 1
DW1_CH_STRUCT26_TR_CMD	0x402986A8	FULL	Channel software trigger

8.2.1.28 CH_STRUCT 27

Register Name	Address	Permission	Description
DW1_CH_STRUCT27_CH_CTL	0x402986C0	FULL	Channel control
DW1_CH_STRUCT27_CH_STATUS	0x402986C4	FULL	Channel status
DW1_CH_STRUCT27_CH_IDX	0x402986C8	FULL	Channel current indices
DW1_CH_STRUCT27_CH_CURR_PTR	0x402986CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT27_INTR	0x402986D0	FULL	Interrupt
DW1_CH_STRUCT27_INTR_SET	0x402986D4	FULL	Interrupt set
DW1_CH_STRUCT27_INTR_MASK	0x402986D8	FULL	Interrupt mask
DW1_CH_STRUCT27_INTR_MASKED	0x402986DC	FULL	Interrupt masked
DW1_CH_STRUCT27_SRAM_DATA0	0x402986E0	FULL	SRAM data 0
DW1_CH_STRUCT27_SRAM_DATA1	0x402986E4	FULL	SRAM data 1
DW1_CH_STRUCT27_TR_CMD	0x402986E8	FULL	Channel software trigger

8.2.1.29 CH_STRUCT 28

Register Name	Address	Permission	Description
DW1_CH_STRUCT28_CH_CTL	0x40298700	FULL	Channel control
DW1_CH_STRUCT28_CH_STATUS	0x40298704	FULL	Channel status
DW1_CH_STRUCT28_CH_IDX	0x40298708	FULL	Channel current indices
DW1_CH_STRUCT28_CH_CURR_PTR	0x4029870C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT28_INTR	0x40298710	FULL	Interrupt
DW1_CH_STRUCT28_INTR_SET	0x40298714	FULL	Interrupt set
DW1_CH_STRUCT28_INTR_MASK	0x40298718	FULL	Interrupt mask
DW1_CH_STRUCT28_INTR_MASKED	0x4029871C	FULL	Interrupt masked
DW1_CH_STRUCT28_SRAM_DATA0	0x40298720	FULL	SRAM data 0
DW1_CH_STRUCT28_SRAM_DATA1	0x40298724	FULL	SRAM data 1
DW1_CH_STRUCT28_TR_CMD	0x40298728	FULL	Channel software trigger

8.2.1.30 CH_STRUCT 29

Register Name	Address	Permission	Description
DW1_CH_STRUCT29_CH_CTL	0x40298740	FULL	Channel control
DW1_CH_STRUCT29_CH_STATUS	0x40298744	FULL	Channel status
DW1_CH_STRUCT29_CH_IDX	0x40298748	FULL	Channel current indices
DW1_CH_STRUCT29_CH_CURR_PTR	0x4029874C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT29_INTR	0x40298750	FULL	Interrupt
DW1_CH_STRUCT29_INTR_SET	0x40298754	FULL	Interrupt set
DW1_CH_STRUCT29_INTR_MASK	0x40298758	FULL	Interrupt mask
DW1_CH_STRUCT29_INTR_MASKED	0x4029875C	FULL	Interrupt masked
DW1_CH_STRUCT29_SRAM_DATA0	0x40298760	FULL	SRAM data 0
DW1_CH_STRUCT29_SRAM_DATA1	0x40298764	FULL	SRAM data 1
DW1_CH_STRUCT29_TR_CMD	0x40298768	FULL	Channel software trigger

8.2.1.31 CH_STRUCT 30

Register Name	Address	Permission	Description
DW1_CH_STRUCT30_CH_CTL	0x40298780	FULL	Channel control
DW1_CH_STRUCT30_CH_STATUS	0x40298784	FULL	Channel status
DW1_CH_STRUCT30_CH_IDX	0x40298788	FULL	Channel current indices
DW1_CH_STRUCT30_CH_CURR_PTR	0x4029878C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT30_INTR	0x40298790	FULL	Interrupt
DW1_CH_STRUCT30_INTR_SET	0x40298794	FULL	Interrupt set
DW1_CH_STRUCT30_INTR_MASK	0x40298798	FULL	Interrupt mask
DW1_CH_STRUCT30_INTR_MASKED	0x4029879C	FULL	Interrupt masked
DW1_CH_STRUCT30_SRAM_DATA0	0x402987A0	FULL	SRAM data 0
DW1_CH_STRUCT30_SRAM_DATA1	0x402987A4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT30_TR_CMD	0x402987A8	FULL	Channel software trigger

8.2.1.32 CH_STRUCT 31

Register Name	Address	Permission	Description
DW1_CH_STRUCT31_CH_CTL	0x402987C0	FULL	Channel control
DW1_CH_STRUCT31_CH_STATUS	0x402987C4	FULL	Channel status
DW1_CH_STRUCT31_CH_IDX	0x402987C8	FULL	Channel current indices
DW1_CH_STRUCT31_CH_CURR_PTR	0x402987CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT31_INTR	0x402987D0	FULL	Interrupt
DW1_CH_STRUCT31_INTR_SET	0x402987D4	FULL	Interrupt set
DW1_CH_STRUCT31_INTR_MASK	0x402987D8	FULL	Interrupt mask
DW1_CH_STRUCT31_INTR_MASKED	0x402987DC	FULL	Interrupt masked
DW1_CH_STRUCT31_SRAM_DATA0	0x402987E0	FULL	SRAM data 0
DW1_CH_STRUCT31_SRAM_DATA1	0x402987E4	FULL	SRAM data 1
DW1_CH_STRUCT31_TR_CMD	0x402987E8	FULL	Channel software trigger

8.2.1.33 CH_STRUCT 32

Register Name	Address	Permission	Description
DW1_CH_STRUCT32_CH_CTL	0x40298800	FULL	Channel control
DW1_CH_STRUCT32_CH_STATUS	0x40298804	FULL	Channel status
DW1_CH_STRUCT32_CH_IDX	0x40298808	FULL	Channel current indices
DW1_CH_STRUCT32_CH_CURR_PTR	0x4029880C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT32_INTR	0x40298810	FULL	Interrupt
DW1_CH_STRUCT32_INTR_SET	0x40298814	FULL	Interrupt set
DW1_CH_STRUCT32_INTR_MASK	0x40298818	FULL	Interrupt mask
DW1_CH_STRUCT32_INTR_MASKED	0x4029881C	FULL	Interrupt masked
DW1_CH_STRUCT32_SRAM_DATA0	0x40298820	FULL	SRAM data 0
DW1_CH_STRUCT32_SRAM_DATA1	0x40298824	FULL	SRAM data 1
DW1_CH_STRUCT32_TR_CMD	0x40298828	FULL	Channel software trigger

8.2.1.34 CH_STRUCT 33

Register Name	Address	Permission	Description
DW1_CH_STRUCT33_CH_CTL	0x40298840	FULL	Channel control
DW1_CH_STRUCT33_CH_STATUS	0x40298844	FULL	Channel status
DW1_CH_STRUCT33_CH_IDX	0x40298848	FULL	Channel current indices
DW1_CH_STRUCT33_CH_CURR_PTR	0x4029884C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT33_INTR	0x40298850	FULL	Interrupt
DW1_CH_STRUCT33_INTR_SET	0x40298854	FULL	Interrupt set
DW1_CH_STRUCT33_INTR_MASK	0x40298858	FULL	Interrupt mask
DW1_CH_STRUCT33_INTR_MASKED	0x4029885C	FULL	Interrupt masked
DW1_CH_STRUCT33_SRAM_DATA0	0x40298860	FULL	SRAM data 0
DW1_CH_STRUCT33_SRAM_DATA1	0x40298864	FULL	SRAM data 1
DW1_CH_STRUCT33_TR_CMD	0x40298868	FULL	Channel software trigger

8.2.1.35 CH_STRUCT 34

Register Name	Address	Permission	Description
DW1_CH_STRUCT34_CH_CTL	0x40298880	FULL	Channel control
DW1_CH_STRUCT34_CH_STATUS	0x40298884	FULL	Channel status
DW1_CH_STRUCT34_CH_IDX	0x40298888	FULL	Channel current indices
DW1_CH_STRUCT34_CH_CURR_PTR	0x4029888C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT34_INTR	0x40298890	FULL	Interrupt
DW1_CH_STRUCT34_INTR_SET	0x40298894	FULL	Interrupt set
DW1_CH_STRUCT34_INTR_MASK	0x40298898	FULL	Interrupt mask
DW1_CH_STRUCT34_INTR_MASKED	0x4029889C	FULL	Interrupt masked
DW1_CH_STRUCT34_SRAM_DATA0	0x402988A0	FULL	SRAM data 0
DW1_CH_STRUCT34_SRAM_DATA1	0x402988A4	FULL	SRAM data 1
DW1_CH_STRUCT34_TR_CMD	0x402988A8	FULL	Channel software trigger

8.2.1.36 CH_STRUCT 35

Register Name	Address	Permission	Description
DW1_CH_STRUCT35_CH_CTL	0x402988C0	FULL	Channel control
DW1_CH_STRUCT35_CH_STATUS	0x402988C4	FULL	Channel status
DW1_CH_STRUCT35_CH_IDX	0x402988C8	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT35_CH_CURR_PTR	0x402988CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT35_INTR	0x402988D0	FULL	Interrupt
DW1_CH_STRUCT35_INTR_SET	0x402988D4	FULL	Interrupt set
DW1_CH_STRUCT35_INTR_MASK	0x402988D8	FULL	Interrupt mask
DW1_CH_STRUCT35_INTR_MASKED	0x402988DC	FULL	Interrupt masked
DW1_CH_STRUCT35_SRAM_DATA0	0x402988E0	FULL	SRAM data 0
DW1_CH_STRUCT35_SRAM_DATA1	0x402988E4	FULL	SRAM data 1
DW1_CH_STRUCT35_TR_CMD	0x402988E8	FULL	Channel software trigger

8.2.1.37 CH_STRUCT 36

Register Name	Address	Permission	Description
DW1_CH_STRUCT36_CH_CTL	0x40298900	FULL	Channel control
DW1_CH_STRUCT36_CH_STATUS	0x40298904	FULL	Channel status
DW1_CH_STRUCT36_CH_IDX	0x40298908	FULL	Channel current indices
DW1_CH_STRUCT36_CH_CURR_PTR	0x4029890C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT36_INTR	0x40298910	FULL	Interrupt
DW1_CH_STRUCT36_INTR_SET	0x40298914	FULL	Interrupt set
DW1_CH_STRUCT36_INTR_MASK	0x40298918	FULL	Interrupt mask
DW1_CH_STRUCT36_INTR_MASKED	0x4029891C	FULL	Interrupt masked
DW1_CH_STRUCT36_SRAM_DATA0	0x40298920	FULL	SRAM data 0
DW1_CH_STRUCT36_SRAM_DATA1	0x40298924	FULL	SRAM data 1
DW1_CH_STRUCT36_TR_CMD	0x40298928	FULL	Channel software trigger

8.2.1.38 CH_STRUCT 37

Register Name	Address	Permission	Description
DW1_CH_STRUCT37_CH_CTL	0x40298940	FULL	Channel control
DW1_CH_STRUCT37_CH_STATUS	0x40298944	FULL	Channel status
DW1_CH_STRUCT37_CH_IDX	0x40298948	FULL	Channel current indices
DW1_CH_STRUCT37_CH_CURR_PTR	0x4029894C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT37_INTR	0x40298950	FULL	Interrupt
DW1_CH_STRUCT37_INTR_SET	0x40298954	FULL	Interrupt set
DW1_CH_STRUCT37_INTR_MASK	0x40298958	FULL	Interrupt mask
DW1_CH_STRUCT37_INTR_MASKED	0x4029895C	FULL	Interrupt masked
DW1_CH_STRUCT37_SRAM_DATA0	0x40298960	FULL	SRAM data 0
DW1_CH_STRUCT37_SRAM_DATA1	0x40298964	FULL	SRAM data 1
DW1_CH_STRUCT37_TR_CMD	0x40298968	FULL	Channel software trigger

8.2.1.39 CH_STRUCT 38

Register Name	Address	Permission	Description
DW1_CH_STRUCT38_CH_CTL	0x40298980	FULL	Channel control
DW1_CH_STRUCT38_CH_STATUS	0x40298984	FULL	Channel status
DW1_CH_STRUCT38_CH_IDX	0x40298988	FULL	Channel current indices
DW1_CH_STRUCT38_CH_CURR_PTR	0x4029898C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT38_INTR	0x40298990	FULL	Interrupt
DW1_CH_STRUCT38_INTR_SET	0x40298994	FULL	Interrupt set
DW1_CH_STRUCT38_INTR_MASK	0x40298998	FULL	Interrupt mask
DW1_CH_STRUCT38_INTR_MASKED	0x4029899C	FULL	Interrupt masked
DW1_CH_STRUCT38_SRAM_DATA0	0x402989A0	FULL	SRAM data 0
DW1_CH_STRUCT38_SRAM_DATA1	0x402989A4	FULL	SRAM data 1
DW1_CH_STRUCT38_TR_CMD	0x402989A8	FULL	Channel software trigger

8.2.1.40 CH_STRUCT 39

Register Name	Address	Permission	Description
DW1_CH_STRUCT39_CH_CTL	0x402989C0	FULL	Channel control
DW1_CH_STRUCT39_CH_STATUS	0x402989C4	FULL	Channel status
DW1_CH_STRUCT39_CH_IDX	0x402989C8	FULL	Channel current indices
DW1_CH_STRUCT39_CH_CURR_PTR	0x402989CC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT39_INTR	0x402989D0	FULL	Interrupt
DW1_CH_STRUCT39_INTR_SET	0x402989D4	FULL	Interrupt set
DW1_CH_STRUCT39_INTR_MASK	0x402989D8	FULL	Interrupt mask
DW1_CH_STRUCT39_INTR_MASKED	0x402989DC	FULL	Interrupt masked
DW1_CH_STRUCT39_SRAM_DATA0	0x402989E0	FULL	SRAM data 0
DW1_CH_STRUCT39_SRAM_DATA1	0x402989E4	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT39_TR_CMD	0x402989E8	FULL	Channel software trigger

8.2.1.41 CH_STRUCT 40

Register Name	Address	Permission	Description
DW1_CH_STRUCT40_CH_CTL	0x40298A00	FULL	Channel control
DW1_CH_STRUCT40_CH_STATUS	0x40298A04	FULL	Channel status
DW1_CH_STRUCT40_CH_IDX	0x40298A08	FULL	Channel current indices
DW1_CH_STRUCT40_CH_CURR_PTR	0x40298A0C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT40_INTR	0x40298A10	FULL	Interrupt
DW1_CH_STRUCT40_INTR_SET	0x40298A14	FULL	Interrupt set
DW1_CH_STRUCT40_INTR_MASK	0x40298A18	FULL	Interrupt mask
DW1_CH_STRUCT40_INTR_MASKED	0x40298A1C	FULL	Interrupt masked
DW1_CH_STRUCT40_SRAM_DATA0	0x40298A20	FULL	SRAM data 0
DW1_CH_STRUCT40_SRAM_DATA1	0x40298A24	FULL	SRAM data 1
DW1_CH_STRUCT40_TR_CMD	0x40298A28	FULL	Channel software trigger

8.2.1.42 CH_STRUCT 41

Register Name	Address	Permission	Description
DW1_CH_STRUCT41_CH_CTL	0x40298A40	FULL	Channel control
DW1_CH_STRUCT41_CH_STATUS	0x40298A44	FULL	Channel status
DW1_CH_STRUCT41_CH_IDX	0x40298A48	FULL	Channel current indices
DW1_CH_STRUCT41_CH_CURR_PTR	0x40298A4C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT41_INTR	0x40298A50	FULL	Interrupt
DW1_CH_STRUCT41_INTR_SET	0x40298A54	FULL	Interrupt set
DW1_CH_STRUCT41_INTR_MASK	0x40298A58	FULL	Interrupt mask
DW1_CH_STRUCT41_INTR_MASKED	0x40298A5C	FULL	Interrupt masked
DW1_CH_STRUCT41_SRAM_DATA0	0x40298A60	FULL	SRAM data 0
DW1_CH_STRUCT41_SRAM_DATA1	0x40298A64	FULL	SRAM data 1
DW1_CH_STRUCT41_TR_CMD	0x40298A68	FULL	Channel software trigger

8.2.1.43 CH_STRUCT 42

Register Name	Address	Permission	Description
DW1_CH_STRUCT42_CH_CTL	0x40298A80	FULL	Channel control
DW1_CH_STRUCT42_CH_STATUS	0x40298A84	FULL	Channel status
DW1_CH_STRUCT42_CH_IDX	0x40298A88	FULL	Channel current indices
DW1_CH_STRUCT42_CH_CURR_PTR	0x40298A8C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT42_INTR	0x40298A90	FULL	Interrupt
DW1_CH_STRUCT42_INTR_SET	0x40298A94	FULL	Interrupt set
DW1_CH_STRUCT42_INTR_MASK	0x40298A98	FULL	Interrupt mask
DW1_CH_STRUCT42_INTR_MASKED	0x40298A9C	FULL	Interrupt masked
DW1_CH_STRUCT42_SRAM_DATA0	0x40298AA0	FULL	SRAM data 0
DW1_CH_STRUCT42_SRAM_DATA1	0x40298AA4	FULL	SRAM data 1
DW1_CH_STRUCT42_TR_CMD	0x40298AA8	FULL	Channel software trigger

8.2.1.44 CH_STRUCT 43

Register Name	Address	Permission	Description
DW1_CH_STRUCT43_CH_CTL	0x40298AC0	FULL	Channel control
DW1_CH_STRUCT43_CH_STATUS	0x40298AC4	FULL	Channel status
DW1_CH_STRUCT43_CH_IDX	0x40298AC8	FULL	Channel current indices
DW1_CH_STRUCT43_CH_CURR_PTR	0x40298ACC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT43_INTR	0x40298AD0	FULL	Interrupt
DW1_CH_STRUCT43_INTR_SET	0x40298AD4	FULL	Interrupt set
DW1_CH_STRUCT43_INTR_MASK	0x40298AD8	FULL	Interrupt mask
DW1_CH_STRUCT43_INTR_MASKED	0x40298ADC	FULL	Interrupt masked
DW1_CH_STRUCT43_SRAM_DATA0	0x40298AE0	FULL	SRAM data 0
DW1_CH_STRUCT43_SRAM_DATA1	0x40298AE4	FULL	SRAM data 1
DW1_CH_STRUCT43_TR_CMD	0x40298AE8	FULL	Channel software trigger

8.2.1.45 CH_STRUCT 44

Register Name	Address	Permission	Description
DW1_CH_STRUCT44_CH_CTL	0x40298B00	FULL	Channel control
DW1_CH_STRUCT44_CH_STATUS	0x40298B04	FULL	Channel status
DW1_CH_STRUCT44_CH_IDX	0x40298B08	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT44_CH_CURR_PTR	0x40298B0C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT44_INTR	0x40298B10	FULL	Interrupt
DW1_CH_STRUCT44_INTR_SET	0x40298B14	FULL	Interrupt set
DW1_CH_STRUCT44_INTR_MASK	0x40298B18	FULL	Interrupt mask
DW1_CH_STRUCT44_INTR_MASKED	0x40298B1C	FULL	Interrupt masked
DW1_CH_STRUCT44_SRAM_DATA0	0x40298B20	FULL	SRAM data 0
DW1_CH_STRUCT44_SRAM_DATA1	0x40298B24	FULL	SRAM data 1
DW1_CH_STRUCT44_TR_CMD	0x40298B28	FULL	Channel software trigger

8.2.1.46 CH_STRUCT 45

Register Name	Address	Permission	Description
DW1_CH_STRUCT45_CH_CTL	0x40298B40	FULL	Channel control
DW1_CH_STRUCT45_CH_STATUS	0x40298B44	FULL	Channel status
DW1_CH_STRUCT45_CH_IDX	0x40298B48	FULL	Channel current indices
DW1_CH_STRUCT45_CH_CURR_PTR	0x40298B4C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT45_INTR	0x40298B50	FULL	Interrupt
DW1_CH_STRUCT45_INTR_SET	0x40298B54	FULL	Interrupt set
DW1_CH_STRUCT45_INTR_MASK	0x40298B58	FULL	Interrupt mask
DW1_CH_STRUCT45_INTR_MASKED	0x40298B5C	FULL	Interrupt masked
DW1_CH_STRUCT45_SRAM_DATA0	0x40298B60	FULL	SRAM data 0
DW1_CH_STRUCT45_SRAM_DATA1	0x40298B64	FULL	SRAM data 1
DW1_CH_STRUCT45_TR_CMD	0x40298B68	FULL	Channel software trigger

8.2.1.47 CH_STRUCT 46

Register Name	Address	Permission	Description
DW1_CH_STRUCT46_CH_CTL	0x40298B80	FULL	Channel control
DW1_CH_STRUCT46_CH_STATUS	0x40298B84	FULL	Channel status
DW1_CH_STRUCT46_CH_IDX	0x40298B88	FULL	Channel current indices
DW1_CH_STRUCT46_CH_CURR_PTR	0x40298B8C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT46_INTR	0x40298B90	FULL	Interrupt
DW1_CH_STRUCT46_INTR_SET	0x40298B94	FULL	Interrupt set
DW1_CH_STRUCT46_INTR_MASK	0x40298B98	FULL	Interrupt mask
DW1_CH_STRUCT46_INTR_MASKED	0x40298B9C	FULL	Interrupt masked
DW1_CH_STRUCT46_SRAM_DATA0	0x40298BA0	FULL	SRAM data 0
DW1_CH_STRUCT46_SRAM_DATA1	0x40298BA4	FULL	SRAM data 1
DW1_CH_STRUCT46_TR_CMD	0x40298BA8	FULL	Channel software trigger

8.2.1.48 CH_STRUCT 47

Register Name	Address	Permission	Description
DW1_CH_STRUCT47_CH_CTL	0x40298BC0	FULL	Channel control
DW1_CH_STRUCT47_CH_STATUS	0x40298BC4	FULL	Channel status
DW1_CH_STRUCT47_CH_IDX	0x40298BC8	FULL	Channel current indices
DW1_CH_STRUCT47_CH_CURR_PTR	0x40298BCC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT47_INTR	0x40298BD0	FULL	Interrupt
DW1_CH_STRUCT47_INTR_SET	0x40298BD4	FULL	Interrupt set
DW1_CH_STRUCT47_INTR_MASK	0x40298BD8	FULL	Interrupt mask
DW1_CH_STRUCT47_INTR_MASKED	0x40298BDC	FULL	Interrupt masked
DW1_CH_STRUCT47_SRAM_DATA0	0x40298BE0	FULL	SRAM data 0
DW1_CH_STRUCT47_SRAM_DATA1	0x40298BE4	FULL	SRAM data 1
DW1_CH_STRUCT47_TR_CMD	0x40298BE8	FULL	Channel software trigger

8.2.1.49 CH_STRUCT 48

Register Name	Address	Permission	Description
DW1_CH_STRUCT48_CH_CTL	0x40298C00	FULL	Channel control
DW1_CH_STRUCT48_CH_STATUS	0x40298C04	FULL	Channel status
DW1_CH_STRUCT48_CH_IDX	0x40298C08	FULL	Channel current indices
DW1_CH_STRUCT48_CH_CURR_PTR	0x40298C0C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT48_INTR	0x40298C10	FULL	Interrupt
DW1_CH_STRUCT48_INTR_SET	0x40298C14	FULL	Interrupt set
DW1_CH_STRUCT48_INTR_MASK	0x40298C18	FULL	Interrupt mask
DW1_CH_STRUCT48_INTR_MASKED	0x40298C1C	FULL	Interrupt masked
DW1_CH_STRUCT48_SRAM_DATA0	0x40298C20	FULL	SRAM data 0
DW1_CH_STRUCT48_SRAM_DATA1	0x40298C24	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT48_TR_CMD	0x40298C28	FULL	Channel software trigger

8.2.1.50 CH_STRUCT 49

Register Name	Address	Permission	Description
DW1_CH_STRUCT49_CH_CTL	0x40298C40	FULL	Channel control
DW1_CH_STRUCT49_CH_STATUS	0x40298C44	FULL	Channel status
DW1_CH_STRUCT49_CH_IDX	0x40298C48	FULL	Channel current indices
DW1_CH_STRUCT49_CH_CURR_PTR	0x40298C4C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT49_INTR	0x40298C50	FULL	Interrupt
DW1_CH_STRUCT49_INTR_SET	0x40298C54	FULL	Interrupt set
DW1_CH_STRUCT49_INTR_MASK	0x40298C58	FULL	Interrupt mask
DW1_CH_STRUCT49_INTR_MASKED	0x40298C5C	FULL	Interrupt masked
DW1_CH_STRUCT49_SRAM_DATA0	0x40298C60	FULL	SRAM data 0
DW1_CH_STRUCT49_SRAM_DATA1	0x40298C64	FULL	SRAM data 1
DW1_CH_STRUCT49_TR_CMD	0x40298C68	FULL	Channel software trigger

8.2.1.51 CH_STRUCT 50

Register Name	Address	Permission	Description
DW1_CH_STRUCT50_CH_CTL	0x40298C80	FULL	Channel control
DW1_CH_STRUCT50_CH_STATUS	0x40298C84	FULL	Channel status
DW1_CH_STRUCT50_CH_IDX	0x40298C88	FULL	Channel current indices
DW1_CH_STRUCT50_CH_CURR_PTR	0x40298C8C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT50_INTR	0x40298C90	FULL	Interrupt
DW1_CH_STRUCT50_INTR_SET	0x40298C94	FULL	Interrupt set
DW1_CH_STRUCT50_INTR_MASK	0x40298C98	FULL	Interrupt mask
DW1_CH_STRUCT50_INTR_MASKED	0x40298C9C	FULL	Interrupt masked
DW1_CH_STRUCT50_SRAM_DATA0	0x40298CA0	FULL	SRAM data 0
DW1_CH_STRUCT50_SRAM_DATA1	0x40298CA4	FULL	SRAM data 1
DW1_CH_STRUCT50_TR_CMD	0x40298CA8	FULL	Channel software trigger

8.2.1.52 CH_STRUCT 51

Register Name	Address	Permission	Description
DW1_CH_STRUCT51_CH_CTL	0x40298CC0	FULL	Channel control
DW1_CH_STRUCT51_CH_STATUS	0x40298CC4	FULL	Channel status
DW1_CH_STRUCT51_CH_IDX	0x40298CC8	FULL	Channel current indices
DW1_CH_STRUCT51_CH_CURR_PTR	0x40298CCC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT51_INTR	0x40298CD0	FULL	Interrupt
DW1_CH_STRUCT51_INTR_SET	0x40298CD4	FULL	Interrupt set
DW1_CH_STRUCT51_INTR_MASK	0x40298CD8	FULL	Interrupt mask
DW1_CH_STRUCT51_INTR_MASKED	0x40298CDC	FULL	Interrupt masked
DW1_CH_STRUCT51_SRAM_DATA0	0x40298CE0	FULL	SRAM data 0
DW1_CH_STRUCT51_SRAM_DATA1	0x40298CE4	FULL	SRAM data 1
DW1_CH_STRUCT51_TR_CMD	0x40298CE8	FULL	Channel software trigger

8.2.1.53 CH_STRUCT 52

Register Name	Address	Permission	Description
DW1_CH_STRUCT52_CH_CTL	0x40298D00	FULL	Channel control
DW1_CH_STRUCT52_CH_STATUS	0x40298D04	FULL	Channel status
DW1_CH_STRUCT52_CH_IDX	0x40298D08	FULL	Channel current indices
DW1_CH_STRUCT52_CH_CURR_PTR	0x40298D0C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT52_INTR	0x40298D10	FULL	Interrupt
DW1_CH_STRUCT52_INTR_SET	0x40298D14	FULL	Interrupt set
DW1_CH_STRUCT52_INTR_MASK	0x40298D18	FULL	Interrupt mask
DW1_CH_STRUCT52_INTR_MASKED	0x40298D1C	FULL	Interrupt masked
DW1_CH_STRUCT52_SRAM_DATA0	0x40298D20	FULL	SRAM data 0
DW1_CH_STRUCT52_SRAM_DATA1	0x40298D24	FULL	SRAM data 1
DW1_CH_STRUCT52_TR_CMD	0x40298D28	FULL	Channel software trigger

8.2.1.54 CH_STRUCT 53

Register Name	Address	Permission	Description
DW1_CH_STRUCT53_CH_CTL	0x40298D40	FULL	Channel control
DW1_CH_STRUCT53_CH_STATUS	0x40298D44	FULL	Channel status
DW1_CH_STRUCT53_CH_IDX	0x40298D48	FULL	Channel current indices

Register Name	Address	Permission	Description
DW1_CH_STRUCT53_CH_CURR_PTR	0x40298D4C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT53_INTR	0x40298D50	FULL	Interrupt
DW1_CH_STRUCT53_INTR_SET	0x40298D54	FULL	Interrupt set
DW1_CH_STRUCT53_INTR_MASK	0x40298D58	FULL	Interrupt mask
DW1_CH_STRUCT53_INTR_MASKED	0x40298D5C	FULL	Interrupt masked
DW1_CH_STRUCT53_SRAM_DATA0	0x40298D60	FULL	SRAM data 0
DW1_CH_STRUCT53_SRAM_DATA1	0x40298D64	FULL	SRAM data 1
DW1_CH_STRUCT53_TR_CMD	0x40298D68	FULL	Channel software trigger

8.2.1.55 CH_STRUCT 54

Register Name	Address	Permission	Description
DW1_CH_STRUCT54_CH_CTL	0x40298D80	FULL	Channel control
DW1_CH_STRUCT54_CH_STATUS	0x40298D84	FULL	Channel status
DW1_CH_STRUCT54_CH_IDX	0x40298D88	FULL	Channel current indices
DW1_CH_STRUCT54_CH_CURR_PTR	0x40298D8C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT54_INTR	0x40298D90	FULL	Interrupt
DW1_CH_STRUCT54_INTR_SET	0x40298D94	FULL	Interrupt set
DW1_CH_STRUCT54_INTR_MASK	0x40298D98	FULL	Interrupt mask
DW1_CH_STRUCT54_INTR_MASKED	0x40298D9C	FULL	Interrupt masked
DW1_CH_STRUCT54_SRAM_DATA0	0x40298DA0	FULL	SRAM data 0
DW1_CH_STRUCT54_SRAM_DATA1	0x40298DA4	FULL	SRAM data 1
DW1_CH_STRUCT54_TR_CMD	0x40298DA8	FULL	Channel software trigger

8.2.1.56 CH_STRUCT 55

Register Name	Address	Permission	Description
DW1_CH_STRUCT55_CH_CTL	0x40298DC0	FULL	Channel control
DW1_CH_STRUCT55_CH_STATUS	0x40298DC4	FULL	Channel status
DW1_CH_STRUCT55_CH_IDX	0x40298DC8	FULL	Channel current indices
DW1_CH_STRUCT55_CH_CURR_PTR	0x40298DCC	FULL	Channel current descriptor pointer
DW1_CH_STRUCT55_INTR	0x40298DD0	FULL	Interrupt
DW1_CH_STRUCT55_INTR_SET	0x40298DD4	FULL	Interrupt set
DW1_CH_STRUCT55_INTR_MASK	0x40298DD8	FULL	Interrupt mask
DW1_CH_STRUCT55_INTR_MASKED	0x40298DDC	FULL	Interrupt masked
DW1_CH_STRUCT55_SRAM_DATA0	0x40298DE0	FULL	SRAM data 0
DW1_CH_STRUCT55_SRAM_DATA1	0x40298DE4	FULL	SRAM data 1
DW1_CH_STRUCT55_TR_CMD	0x40298DE8	FULL	Channel software trigger

8.2.1.57 CH_STRUCT 56

Register Name	Address	Permission	Description
DW1_CH_STRUCT56_CH_CTL	0x40298E00	FULL	Channel control
DW1_CH_STRUCT56_CH_STATUS	0x40298E04	FULL	Channel status
DW1_CH_STRUCT56_CH_IDX	0x40298E08	FULL	Channel current indices
DW1_CH_STRUCT56_CH_CURR_PTR	0x40298E0C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT56_INTR	0x40298E10	FULL	Interrupt
DW1_CH_STRUCT56_INTR_SET	0x40298E14	FULL	Interrupt set
DW1_CH_STRUCT56_INTR_MASK	0x40298E18	FULL	Interrupt mask
DW1_CH_STRUCT56_INTR_MASKED	0x40298E1C	FULL	Interrupt masked
DW1_CH_STRUCT56_SRAM_DATA0	0x40298E20	FULL	SRAM data 0
DW1_CH_STRUCT56_SRAM_DATA1	0x40298E24	FULL	SRAM data 1
DW1_CH_STRUCT56_TR_CMD	0x40298E28	FULL	Channel software trigger

8.2.1.58 CH_STRUCT 57

Register Name	Address	Permission	Description
DW1_CH_STRUCT57_CH_CTL	0x40298E40	FULL	Channel control
DW1_CH_STRUCT57_CH_STATUS	0x40298E44	FULL	Channel status
DW1_CH_STRUCT57_CH_IDX	0x40298E48	FULL	Channel current indices
DW1_CH_STRUCT57_CH_CURR_PTR	0x40298E4C	FULL	Channel current descriptor pointer
DW1_CH_STRUCT57_INTR	0x40298E50	FULL	Interrupt
DW1_CH_STRUCT57_INTR_SET	0x40298E54	FULL	Interrupt set
DW1_CH_STRUCT57_INTR_MASK	0x40298E58	FULL	Interrupt mask
DW1_CH_STRUCT57_INTR_MASKED	0x40298E5C	FULL	Interrupt masked
DW1_CH_STRUCT57_SRAM_DATA0	0x40298E60	FULL	SRAM data 0
DW1_CH_STRUCT57_SRAM_DATA1	0x40298E64	FULL	SRAM data 1

Register Name	Address	Permission	Description
DW1_CH_STRUCT57_TR_CMD	0x40298E68	FULL	Channel software trigger

8.3 Register Details

8.3.1 DW_CTL

Description: Control
Address: 0x40280000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						ECC_INJ_EN [1:1]	ECC_EN [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ECC_EN	RW	RW	1	Enable ECC checking: '0': Disabled. '1': Enabled.
1	ECC_INJ_EN	RW	RW	0	Enable parity injection for SRAM. When '1', the parity (ECC_CTL.PARITY) is used when a full 32-bit write is done to the ECC_CTL.WORD_ADDR word address of the SRAM.
31	ENABLED	RW	RW	0	IP enable: '0': Disabled. Disabling the IP activates the IP's Active logic reset: Active logic and non-retention MMIO registers are reset (retention MMIO registers are not affected). '1': Enabled.

8.3.2 DW_STATUS

Description: Status
Address: 0x40280004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:3]	B [2:2]	NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				PREEMPTABLE [11:11]	None [10:10]	PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	CH_IDX [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ACTIVE [31:31]	STATE [30:28]			None [27:25]			CH_IDX [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	R	R	Undefined	Active channel, user/privileged access control: '0': user mode. '1': privileged mode.
1	NS	R	R	Undefined	Active channel, secure/non-secure access control: '0': secure. '1': non-secure.
2	B	R	R	Undefined	Active channel, non-bufferable/bufferable access control: '0': non-bufferable '1': bufferable.
4:7	PC	R	R	Undefined	Active channel protection context.
8:9	PRIO	R	R	Undefined	Active channel priority.
11	PREEMPTABLE	R	R	Undefined	Active channel preemptable.
16:24	CH_IDX	R	R	Undefined	Active channel index.
28:30	STATE	R	R	0	State of the DW controller. '0': Default/inactive state. '1': Loading descriptor. '2': Loading data element from source location. '3': Storing data element to destination location. '4': CRC functionality (only used for CRC transfer descriptor type). '5': Update of active control information (e.g. source and destination addresses) and wait for trigger de-activation. '6': Error.
31	ACTIVE	R	R	0	Active channel present: '0': No. '1': Yes.

8.3.3 DW_ACT_DESCR_CTL

Description: Active descriptor control
Address: 0x40280020
Offset: 0x20
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Copy of DESCR_CTL of the currently active descriptor. [1:0] WAIT_FOR_DEACT Specifies whether the controller should wait for the input trigger to be deactivated; i.e. the selected system trigger is not active. This field is used to synchronize the controller with the agent that generated the trigger. This field is ONLY used at the completion of the transfer as specified by TR_IN. E.g., a TX FIFO indicates that it is empty and it needs a new data sample. The agent removes the trigger ONLY when the data sample has been written by the controller AND received by the agent. Furthermore, the agent's trigger may be delayed by a few cycles before it reaches the controller. This field is used for level sensitive trigger, which reflect state (pulse sensitive triggers should have this field set to '0'). The wait cycles incurred by this field reduce DW controller performance. '0': Do not wait for trigger de-activation (for pulse sensitive triggers). '1': Wait for up to 4 cycles. '2': Wait for up to 16 cycles. '3': Wait indefinitely. This option may result in controller lockup if the trigger is not de-activated. [3:2] INTR_TYPE Specifies the input trigger type (not to be confused with the descriptor type): '0': A trigger results in the execution of a single transfer. The descriptor type can be single, 1D or 2D. '1': A trigger results in the execution of a single 1D transfer. - If the descriptor type is 'single', the trigger results in the execution of a single transfer. - If the descriptor type is '1D' or '2D', the trigger results in the execution of a 1D transfer. '2': A trigger results in the execution of the current descriptor. '3': A trigger results in the execution of the current descriptor and continues (without requiring another input trigger) with the execution of the next descriptor using the next descriptor's information. [5:4] TR_OUT_TYPE Specifies when an output trigger is generated: '0': An output trigger is generated after a single transfer. '1': An output trigger is generated after a single 1D transfer. - If the descriptor type is 'single', the output trigger is generated after a single transfer. - If the descriptor type is '1D', 'CRC' or '2D', the output trigger is generated after the execution of a 1D transfer. '2': An output trigger is generated after the execution of the current descriptor. '3': An output trigger is generated after the execution of a descriptor list: after the execution of the current descriptor AND the current descriptor DESCR_NEXT_PTR.ADDR is '0'. [7:6] TR_IN_TYPE Specifies the input trigger type (not to be confused with the descriptor type). '0': A trigger results in the execution of a single transfer. The descriptor type can be single, 1D or 2D. '1': A trigger results in the execution of a single 1D transfer.

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) - If the descriptor type is 'single', the trigger results in the execution of a single transfer. - If the descriptor type is '1D' or '2D', the trigger results in the execution of a 1D transfer. '2': A trigger results in the execution of the current descriptor. '3': A trigger results in the execution of the current descriptor and continues (without requiring another input trigger) with the execution of the next descriptor using the next descriptor's information. [24] CH_DISABLE Specifies whether the channel is disabled or not after completion of the current descriptor (independent of the value of the DESCR_NEXT_PTR value): '0': Channel is not disabled. '1': Channel is disabled. Note: a disabled channel will ignore its input trigger. [26] SRC_TRANSFER_SIZE Specifies the bus transfer size to the source location: '0': As specified by DATA_SIZE. '1': Word (32 bits). Distinguishing bus transfer size from data element size allows for source components with data elements that are smaller than their 32-bit bus interface width. E.g., an ADC source has a 32-bit bus transfer size, but only provides a 16-bit data element. [27] DST_TRANSFER_SIZE Specifies the bus transfer size to the destination location: '0': As specified by DATA_SIZE. '1': Word (32 bits). Distinguishing bus transfer size from data element size allows for destination components with data elements that are smaller than their 32-bit bus interface width. E.g., a DAC destination has a 32-bit bus transfer size, but only requires a 16-bit data element. [29:28] DATA_SIZE Specifies the data element size: '0': Byte (8 bits). '1': Halfword (16 bits). '2': Word (32 bits). DATA_SIZE, SRC_TRANSFER_SIZE and DST_TRANSFER_SIZE together determine how data elements are transferred. The following are the 9 legal settings: - DATA is 8 bit, SRC is 8 bit, DST is 8 bit. - DATA is 8 bit, SRC is 32 bit (higher 24 bits are dropped), DST is 8 bit. - DATA is 8 bit, SRC is 8 bit, DST is 32 bit (higher 24 bits are made '0'). - DATA is 8 bit, SRC is 32 bit (higher 24 bits are dropped), DST is 32 bit (higher 24 bits are made '0'). - DATA is 16 bit, SRC is 16 bit, DST is 16 bit. - DATA is 16 bit, SRC is 32 bit (higher 16 bits are dropped), DST is 16 bit. - DATA is 16 bit, SRC is 16 bit, DST is 32 bit (higher 16 bits are made '0'). - DATA is 16 bit, SRC is 32 bit (higher 16 bits are dropped), DST is 32 bit (higher 16 bits are made '0'). - DATA is 32 bit, SRC is 32 bit, DST is 32-bit. [31:30] DESCR_TYPE Specifies the descriptor type (not to be confused with the trigger type): '0': Single transfer. The DESCR_X_CTL and DESCR_Y_CTL registers are not present and DESCR_NEXT_PTR is at offset 0x0c.

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) '1': 1D transfer. The DESCR_X_CTL register is present, the DESCR_Y_CTL is not present and DESCR_NEXT_PTR is at offset 0x10. A 1D transfer consists out of DESCR_X_CTL.X_COUNT single transfers. '2': 2D transfer. The DESCR_X_CTL and DESCR_Y_CTL registers are present and DESCR_NEXT_PTR is at offset 0x14. A 2D transfer consists of $\text{DESCR\_X\_CTL.X\_COUNT} \times \text{DESCR\_Y\_CTL.Y\_COUNT}$ single transfers. '3': CRC transfer. The DESCR_X_CTL register is present, the DESCR_Y_CTL is not present and DESCR_NEXT_PTR is at offset 0x10. A CRC transfer consists out of DESCR_X_CTL.X_COUNT single transfers. After the execution of the current descriptor, the DESCR_NEXT_PTR address is copied to the channel's CH_CURR_PTR address and CH_STATUS.X_IDX and CH_STATUS.Y_IDX are set to '0'.

8.3.4 DW_ACT_DESCR_SRC

Description: Active descriptor source
Address: 0x40280024
Offset: 0x24
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Copy of DESCR_SRC of the currently active descriptor. Base address of source location.

8.3.5 DW_ACT_DESCR_DST

Description: Active descriptor destination
Address: 0x40280028
Offset: 0x28
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Copy of DESCR_DST of the currently active descriptor. Base address of destination location. Note: For a CRC transfer descriptor, this field should be programmed with the address of the CRC_LFSR_CTL register. The calculated CRC LFSR state is written to this address (through the CRYPTO AHB-Lite master interface) when the input trigger is processed. The write transfer will be submitted to the CPUSS and PERI protection schemes.

8.3.6 DW_ACT_DESCR_X_CTL

Description: Active descriptor X loop control
Address: 0x40280030
Offset: 0x30
Retention: Not Retained
IsDeepSleep: No
Comment: If the currently active descriptor has not X_CTL register, this MMIO register provides undefined information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Copy of DESCR_X_CTL of the currently active descriptor. [11:0] SRC_X_INCR Specifies increment of source address for each X loop iteration (in multiples of SRC_TRANSFER_SIZE). This field is a signed number in the range [-2048, 2047]. If this field is '0', the source address is not incremented. This is useful for reading from RX FIFO structures. [23:12] DST_X_INCR Specifies increment of destination address for each X loop iteration (in multiples of DST_TRANSFER_SIZE). This field is a signed number in the range [-2048, 2047]. If this field is '0', the destination address is not incremented. This is useful for writing to TX FIFO structures. Note: this field is not used for CRC transfer descriptors and must be set to '0'. [31:24] X_COUNT Number of iterations (minus 1) of the 'X loop' (X_COUNT+1 is the number of single transfers in a 1D transfer). This field is an unsigned number in the range [0, 255], representing 1 through 256 iterations. For a single transfer descriptor type, descriptor will not have X_CTL.

8.3.7 DW_ACT_DESCR_Y_CTL

Description: Active descriptor Y loop control
Address: 0x40280034
Offset: 0x34
Retention: Not Retained
IsDeepSleep: No
Comment: If the currently active descriptor has not Y_CTL register, this MMIO register provides undefined information.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Copy of DESCR_Y_CTL of the currently active descriptor. [11:0] SRC_Y_INCR Specifies increment of source address for each Y loop iteration (in multiples of SRC_TRANSFER_SIZE). This field is a signed number in the range [-2048, 2047]. [23:12] DST_Y_INCR Specifies increment of destination address for each Y loop iteration (in multiples of DST_TRANSFER_SIZE). This field is a signed number in the range [-2048, 2047]. [31:24] Y_COUNT Number of iterations (minus 1) of the 'Y loop' $(X\_COUNT+1)*(Y\_COUNT+1)$ is the number of single transfers in a 2D transfer). This field is an unsigned number in the range [0, 255], representing 1 through 256 iterations. For single, 1D and CRC transfer descriptor types, descriptor will not have Y_CTL.

8.3.8 DW_ACT_DESCR_NEXT_PTR

Description: Active descriptor next pointer
Address: 0x40280038
Offset: 0x38
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	ADDR	R	R	Undefined	Copy of DESCR_NEXT_PTR of the currently active descriptor. [31:2] ADDR Address of next descriptor in descriptor list. When this field is '0', this is the last descriptor in the descriptor list.

8.3.9 DW_ACT_SRC

Description: Active source
Address: 0x40280040
Offset: 0x40
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SRC_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SRC_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SRC_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SRC_ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SRC_ADDR	R	R	Undefined	Current address of source location.

8.3.10 DW_ACT_DST

Description: Active destination
Address: 0x40280044
Offset: 0x44
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DST_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DST_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DST_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DST_ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DST_ADDR	R	R	Undefined	Current address of destination location.

8.3.11 DW_ECC_CTL

Description: ECC control
Address: 0x40280080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORD_ADDR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						WORD_ADDR [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	PARITY [31:25]							None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	WORD_ADDR	RW	RW	0	Specifies the word address where an error will be injected. - On a write transfer to this SRAM word address and when CTL.ECC_INJ_EN bit is '1', the parity (PARITY) is injected.
25:31	PARITY	RW	RW	0	ECC parity to use for ECC error injection at address WORD_ADDR.

8.3.12 DW_CRC_CTL

Description: CRC control
Address: 0x40280100
Offset: 0x100
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							DATA_REVERSE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							REM_REVERSE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DATA_REVERSE	RW	RW	0	Specifies the bit order in which a data Byte is processed (reversal is performed after XORing): '0': Most significant bit (bit 1) first. '1': Least significant bit (bit 0) first.
8	REM_REVERSE	RW	RW	0	Specifies whether the remainder is bit reversed (reversal is performed after XORing): '0': No. '1': Yes.

8.3.13 DW_CRC_DATA_CTL

Description: CRC data control
Address: 0x40280110
Offset: 0x110
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA_XOR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA_XOR	RW	RW	0	Specifies a byte mask with which each data byte is XOR'd. The XOR is performed before data reversal.

8.3.14 DW_CRC_POL_CTL

Description: CRC polynomial control
Address: 0x40280120
Offset: 0x120
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	POLYNOMIAL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	POLYNOMIAL [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	POLYNOMIAL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	POLYNOMIAL [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	POLYNOMIAL	RW	RW	0	CRC polynomial. The polynomial is represented WITHOUT the high order bit (this bit is always assumed '1'). The polynomial should be aligned/shifted such that the more significant bits (bit 31 and down) contain the polynomial and the less significant bits (bit 0 and up) contain padding '0's. Some frequently used polynomials: - CRC32: POLYNOMIAL is 0x04c11db7 ($x^{32} + x^{26} + x^{23} + x^{22} + x^{16} + x^{12} + x^{11} + x^{10} + x^8 + x^7 + x^5 + x^4 + x^2 + x + 1$). - CRC16: POLYNOMIAL is 0x80050000 ($x^{16} + x^{15} + x^2 + 1$, shifted by 16 bit positions). - CRC16 CCITT: POLYNOMIAL is 0x10210000 ($x^{16} + x^{12} + x^5 + 1$, shifted by 16 bit positions).

8.3.15 DW_CRC_LFSR_CTL

Description: CRC LFSR control
Address: 0x40280130
Offset: 0x130
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LFSR32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LFSR32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LFSR32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	LFSR32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	LFSR32	RW	RW	0	State of a 32-bit Linear Feedback Shift Registers (LFSR) that is used to implement CRC. This register needs to be initialized by SW to provide the CRC seed value. The seed value should be aligned such that the more significant bits (bit 31 and down) contain the seed value and the less significant bits (bit 0 and up) contain padding '0's. Note that SW can write this field. This functionality can be used prevent information leakage (through either CRC_LFSR_CTL or CRC_REM_RESULT).

8.3.16 DW_CRC_REM_CTL

Description: CRC remainder control
Address: 0x40280140
Offset: 0x140
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REM_XOR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REM_XOR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REM_XOR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REM_XOR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REM_XOR	RW	RW	0	Specifies a mask with which the CRC_LFSR_CTL.LFSR32 register is XOR'd to produce a remainder. The XOR is performed before remainder reversal.

8.3.17 DW_CRC_REM_RESULT

Description: CRC remainder result
Address: 0x40280148
Offset: 0x148
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REM	R	R	0	Remainder value. The alignment of the remainder depends on CRC_REM_CTL0.REM_REVERSE: '0': the more significant bits (bit 31 and down) contain the remainder. '1': the less significant bits (bit 0 and up) contain the remainder. Note: This field is combinatorially derived from CRC_LFSR_CTL.LFSR32, CRC_CTL.REM_REVERSE and CRC_REM_CTL.REM_XOR.

8.3.18 CH_STRUCT

8.3.18.1 DW_CH_STRUCT_CH_CTL

Description: Channel control
Address: 0x40288000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:3]	B [2:2]	NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				PREEMPTAB LE [11:11]	None [10:10]	PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	Undefined	User/privileged access control: '0': user mode. '1': privileged mode. This field is set with the user/privileged access control of the transaction that writes this register; i.e. the 'write data' is ignored and instead the access control is inherited from the write transaction (note the field attributes should be HW:RW, SW:R). All transactions for this channel use the P field for the user/privileged access control ('hprot[1]').
1	NS	RW	RW	Undefined	Secure/on-secure access control: '0': secure. '1': non-secure. This field is set with the secure/non-secure access control of the transaction that writes this register; i.e. the 'write data' is ignored and instead the access control is inherited from the write transaction (note the field attributes should be HW:RW, SW:R). All transactions for this channel use the NS field for the secure/non-secure access control ('hprot[4]').

Bits	Name	SW	HW	Default or Enum	Description
2	B	RW	RW	Undefined	Non-bufferable/bufferable access control: '0': non-bufferable. '1': bufferable. This field is used to indicate to an AMBA bridge that a write transaction can complete without waiting for the destination to accept the write transaction data. All transactions for this channel uses the B field for the non-bufferable/bufferable access control ('hprot[2]').
4:7	PC	RW	RW	Undefined	Protection context. This field is set with the protection context of the transaction that writes this register; i.e. the 'write data' is ignored and instead the context is inherited from the write transaction (note the field attributes should be HW:RW, SW:R). All transactions for this channel uses the PC field for the protection context.
8:9	PRI0	RW	RW	0	Channel priority: '0': highest priority. '1' '2' '3': lowest priority. Channels with the same priority constitute a priority group. Priority decoding determines the highest priority pending channel. This channel is determined as follows. First, the highest priority group with pending channels is identified. Second, within this priority group, round robin arbitration is applied. Round robin arbitration (within a priority group) gives the highest priority to the lower channel indices (within the priority group).
11	PREEMPTABLE	RW	RW	Undefined	Specifies if the channel is preemptable. '0': Not preemptable. '1': Preemptable. This field allows higher priority pending channels (from a higher priority group; i.e. an active channel can NOT be preempted by a pending channel in the same priority group) to preempt the active channel in between 'single transfers' (a 1D transfer consists out of X_COUNT single transfers; a 2D transfer consists out of X_COUNT*Y_COUNT single transfers). Preemption will NOT affect the pending status of channel. As a result, after completion of a higher priority activated channel, the current channel may be reactivated.
31	ENABLED	RW	RW	0	Channel enable: '0': Disabled. The channel's trigger is ignored and the channel cannot be made pending and therefore cannot be made active. If a pending channel is disabled, the channel is made non pending. If the activate channel is disabled, the channel is de-activated (bus transactions are completed). '1': Enabled. SW sets this field to '1' to enable a specific channel. HW sets this field to '0' on an error interrupt cause (the specific error is specified by CH_STATUS.INTR_CAUSE).

8.3.18.2 DW_CH_STRUCT_CH_STATUS

Description: Channel status
Address: 0x40288004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				INTR_CAUSE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PENDING [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	INTR_CAUSE	R	R	Undefined	Specifies the source of the interrupt cause: '0': No interrupt generated '1': Interrupt based on transfer completion configuration based on INTR_TYPE '2': Source transfer bus error '3': Destination transfer bus error '4': Source address misalignment '5': Destination address misalignment '6': Current descriptor pointer is null '7': Active channel is disabled '8': Descriptor bus error '9'-'15': Not used. For error related interrupt causes (INTR_CAUSE is '2', '3', ..., '8'), the channel is disabled (HW sets CH_CTL.ENABLED to '0').
31	PENDING	R	R	0	Specifies pending DW channels; i.e. enabled channels whose trigger got activated. This field includes all channels that are in the pending state (not scheduled) or active state (scheduled and performing data transfer(s)).

8.3.18.3 DW_CH_STRUCT_CH_IDX

Description: Channel current indices
Address: 0x40288008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: Note that this register is retained during DeepSleep system power mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	X_IDX [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	Y_IDX [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	X_IDX	RW	RW	Undefined	Specifies the X loop index. In the range of [0, X_COUNT], with X_COUNT taken from the current descriptor. Note: HW sets this field to '0' when it updates the current descriptor pointer CH_CURR_PTR with DESCR_NEXT_PTR after execution of the current descriptor. Note: SW should set this field to '0' when it updates CH_CURR_PTR.
8:15	Y_IDX	RW	RW	Undefined	Specifies the Y loop index, with X_COUNT taken from the current descriptor. Note: HW sets this field to '0' when it updates the current descriptor pointer CH_CURR_PTR with DESCR_NEXT_PTR after execution of the current descriptor. Note: SW should set this field to '0' when it updates CH_CURR_PTR.

8.3.18.4 DW_CH_STRUCT_CH_CURR_PTR

Description: Channel current descriptor pointer
Address: 0x4028800C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	ADDR	RW	RW	Undefined	Address of current descriptor. When this field is '0', there is no valid descriptor. Note: HW updates the current descriptor pointer CH_CURR_PTR with DESCR_NEXT_PTR after execution of the current descriptor. Note: Typically, when SW updates the current descriptor pointer CH_CURR_PTR, it also sets CH_IDX.X_IDX and CH_IDX.Y_IDX to '0'.

8.3.18.5 DW_CH_STRUCT_INTR

Description: Interrupt
Address: 0x40288010
Offset: 0x10
Retention: Not Retained
IsDeepSleep: No
Comment: The register fields are not retained. This is to ensure that they come up as '0' after coming out of DeepSleep system power mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							CH [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CH	RW1C	RW1C	0	Set to '1', when event (as specified by CH_STATUS.INTR_CAUSE) is detected. Write INTR.CH field with '1', to clear bit. Write INTR_SET.CH field with '1', to set bit.

8.3.18.6 DW_CH_STRUCT_INTR_SET

Description: Interrupt set
Address: 0x40288014
Offset: 0x14
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the INTR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							CH [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CH	RW1S	RW1S	0	Write INTR_SET field with '1' to set corresponding INTR.CH field (a write of '0' has no effect).

8.3.18.7 DW_CH_STRUCT_INTR_MASK

Description: Interrupt mask
Address: 0x40288018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							CH [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CH	RW	RW	0	Mask for corresponding field in INTR register.

8.3.18.8 DW_CH_STRUCT_INTR_MASKED

Description: Interrupt masked
Address: 0x4028801C
Offset: 0x1C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise AND between the INTR and INTR_MASK registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for INTR and one for INTR_MASK. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_MASKED != 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							CH [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CH	R	R	0	Logical and of corresponding INTR and INTR_MASK fields.

8.3.18.9 DW_CH_STRUCT_SRAM_DATA0

Description: SRAM data 0
Address: 0x40288020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: SRAM_DATA0 and SRAM_DATA1 are provided for ECC fault injection functionality. These register should NOT be used to control regular functionality (except that they can be used for initialization of DW SRAMs).

Some of the CH_CTL, CH_STATUS, CH_IDX and CH_CURR_PTR fields are implemented using SRAM storage. Each channel uses two 32-bit SRAM data words. The fields of a register that are implemented using SRAM storage are mapped on a subset of either of the two 32-bit SRAM data words. Specifically, the first 32-bit SRAM data word implements CH_CTL.P, CH_CTL.NS, CH_CTL.B, CH_CTL.PC, CH_CTL.PREEMPTABLE, CH_IDX.X_IDX and CH_IDX.Y_IDX fields and the second 32-bit SRAM data word implements the CH_CURR_PTR.ADDR field. As a result, CH_CTL, CH_IDX and CH_CURR_PTR writes only update a subset of a 32-bit SRAM data word.

For ECC fault injection, it is required to update a complete 32-bit SRAM data word with a user provided ECC parity (specified by ECC_CTL.PARITY) at a specific SRAM location (specified by ECC_CTL.WORD_ADDR). Therefore, SRAM_DATA0 and SRAM_DATA1 provide access to specific SRAM locations. For a channel i , SRAM_DATA0 provides access to SRAM word address $2*i$ and SRAM_DATA1 provides access to SRAM word address $2*i + 1$. E.g., to inject a fault at SRAM word address '13', CTL.ECC_INJ_EN is set to '1', ECC_CTL.WORD_ADDR is set to '13', and ECC_CTL.PARITY is set to the faulting parity. Next, the SW performs a 32-bit write to SRAM_DATA1 of channel 6 ($2*6 + 1 = 13$). The write data and the faulting parity is written to SRAM word address '13'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	Undefined	N/A

8.3.18.10 DW_CH_STRUCT_SRAM_DATA1

Description: SRAM data 1
Address: 0x40288024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	Undefined	N/A

8.3.18.11 DW_CH_STRUCT_TR_CMD

Description: Channel software trigger
Address: 0x40288028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ACTIVATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ACTIVATE	RW1S	RW1S	0	Software trigger. When written with '1', a trigger is generated which sets 'trigger pending' (only if the channel is enabled). A read always returns a 0.

9 EFUSE

Description EFUSE MXS40 registers
Base Address 0x402C0000
Size 0x200
Slave Num MMIO2 - 10

10 EFUSE_DATA

Description eFUSE memory
Base Address 0x402C0800
Size 0x200
Slave Num MMIO2 - 10

Register Name	Address	Permission	Description
EFUSE_DATA_CUSTOMER_DATA0	0x402C0868	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
EFUSE_DATA_CUSTOMER_DATA1	0x402C086C	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
EFUSE_DATA_CUSTOMER_DATA2	0x402C0870	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
EFUSE_DATA_CUSTOMER_DATA3	0x402C0874	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
EFUSE_DATA_CUSTOMER_DATA4	0x402C0878	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
EFUSE_DATA_CUSTOMER_DATA5	0x402C087C	NO-ACCESS	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.

10.1 Register Details

10.1.1 EFUSE_DATA_CUSTOMER_DATA

Description:	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.
Address:	0x402C0868
Offset:	0x68
Retention:	Retained
IsDeepSleep:	No
Comment:	The eFUSE memory consists of an array of eFUSE macros. The memory can only be read with AHB-Lite Byte read transfers. A non-Byte AHB-Lite read transfer results in an AHB-Lite bus error. An AHB-Lite write transfer results in an AHB-Lite bus error. Furthermore, an AHB-Lite read transfer while a program operation is in progress (CMD.START is '1') results in an AHB-Lite bus error.
	The number of eFUSE memory Bytes is determined by the EFUSE_NR configuration parameter. This parameter specifies the number of instantiated eFUSE macros. Each macro has 16 Bytes. E.g., if EFUSE_NR is 8, the eFUSE memory has 8*16 Bytes = 128 Bytes.
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA_BYTE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA_BYTE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA_BYTE [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA_BYTE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA_BYTE	RW	RW	0	Available EFUSE bits for customer usage. They can be programmed in NORMAL protection state via CMx/DAP and in SECURE protection state via CMx.

11 ETH

Description Ethernet Interface
Base Address 0x40480000
Size 0x10000
Slave Num MMIO4 - 2

Register Name	Address	Permission	Description
ETH0_CTL	0x40480000	FULL	MXETH Control Register
ETH0_STATUS	0x40480004	FULL	MXETH Status Register
ETH0_NETWORK_CONTROL	0x40481000	FULL	The network control register contains general MAC control functions for both receiver and transmitter.
ETH0_NETWORK_CONFIG	0x40481004	FULL	The network configuration register contains functions for setting the mode of operation for the Gigabit Ethernet MAC.
ETH0_NETWORK_STATUS	0x40481008	FULL	The network status register returns status information with respect to the PHY management interface.
ETH0_USER_IO_REGISTER	0x4048100C	FULL	Not presents. Access to the register will return AHB error.
ETH0_DMA_CONFIG	0x40481010	FULL	DMA Configuration Register
ETH0_TRANSMIT_STATUS	0x40481014	FULL	This register, when read, provides details of the status of a transmit. Once read, individual bits may be cleared by writing 1 to them. It is not possible to set a bit to 1 by writing to the register.
ETH0_RECEIVE_Q_PTR	0x40481018	FULL	This register holds the start address of the receive buffer queue (receive buffers descriptor list). The receive buffer queue base address must be initialized before receive is enabled through bit 2 of the network control register. Once reception is enabled, any write to the receive buffer queue base address register is ignored. Reading this register returns the location of the descriptor currently being accessed. This value increments as buffers are used. Software should not use this register for determining where to remove received frames from the queue as it constantly changes as new frames are received. Software should instead work its way through the buffer descriptor queue checking the used bits. In terms of AMBA (AXI) operation, the receive descriptors are read from memory using a single 32bit AXI access. When the datapath is configured at 64bit, the receive descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is written to using a single 64bit AXI access.

Register Name	Address	Permission	Description
ETH0_TRANSMIT_Q_PTR	0x4048101C	FULL	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.
ETH0_RECEIVE_STATUS	0x40481020	FULL	This register, when read provides details of the status of a receive. Once read, individual bits may be cleared by writing 1 to them. It is not possible to set a bit to 1 by writing to the register.
ETH0_INT_STATUS	0x40481024	FULL	If not configured for priority queueing, the GEM generates a single interrupt. This register indicates the source of this interrupt. The corresponding bit in the mask register must be clear for a bit to be set. If any bit is set in this register the ethernet_int signal will be asserted. For test purposes each bit can be set or reset by writing to the interrupt mask register. The default configuration is shown below whereby all bits are reset to zero on read. Changing the validity of the 'gem_irq_read_clear' define will instead require a one to be written to the appropriate bit in order to clear it. In this mode reading has no affect on the status of the bit.
ETH0_INT_ENABLE	0x40481028	FULL	At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.
ETH0_INT_DISABLE	0x4048102C	FULL	Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.
ETH0_INT_MASK	0x40481030	FULL	The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.

Register Name	Address	Permission	Description
ETH0_PHY_MANAGEMENT	0x40481034	FULL	The PHY maintenance register is implemented as a shift register. Writing to the register starts a shift operation which is signalled as complete when bit-2 is set in the network status register. It takes about 2000 pclk cycles to complete, when MDC is set for pclk divide by 32 in the network configuration register. An interrupt is generated upon completion. During this time, the MSB of the register is output on the MDIO pin and the LSB updated from the MDIO pin with each MDC cycle. This causes transmission of a PHY management frame on MDIO. See Section 22.2.4.5 of the IEEE 802.3 standard. Reading during the shift operation will return the current contents of the shift register. At the end of management operation, the bits will have shifted back to their original locations. For a read operation, the data bits will be updated with data read from the PHY. It is important to write the correct values to the register to ensure a valid PHY management frame is produced. The MDIO interface can read IEEE 802.3 clause 45 PHYs as well as clause 22 PHYs. To read clause 45 PHYs, bit 30 should be written with a 0 rather than a 1. For a description of MDC generation, see Network Configuration Register.
ETH0_PAUSE_TIME	0x40481038	FULL	Received Pause Quantum Register
ETH0_TX_PAUSE_QUANTUM	0x4048103C	FULL	Transmit Pause Quantum Register
ETH0_PBUF_TXCUTTHRU	0x40481040	FULL	Partial store and forward is only applicable when using the DMA configured in SRAM based packet buffer mode. It is also not available when using multi buffer frames. TX Partial Store and Forward
ETH0_PBUF_RXCUTTHRU	0x40481044	FULL	RX Partial Store and Forward
ETH0_JUMBO_MAX_LENGTH	0x40481048	FULL	Maximum Jumbo Frame Size.
ETH0_EXTERNAL_FIFO_INTERFACE	0x4048104C	FULL	Not presents.
ETH0_RSC_CONTROL	0x40481058	FULL	Not presents. Access to the register will return AHB error.
ETH0_INT_MODERATION	0x4048105C	FULL	Used to moderate the number of transmit and receive complete interrupts issued. With interrupt moderation enabled receive and transmit interrupts are not generated immediately a frame is transmitted or received. Instead when a receive or transmit event occurs a timer is started and the interrupt is asserted after it times out. This limits the frequency with which the CPU receives interrupts. When interrupt moderation is enabled interrupt status bit one is always used for receive and bit 7 is always used for transmit even when priority queuing is enabled. With interrupt moderation 800ns periods are counted. GEM determines what constitutes an 800ns period by looking at the tbi (bit 11), gigabit bit (10) and speed (bit 0) bits in the network configuration register and counting tx_clk cycles. Bit 0 needs to be set to 1 for 100M operation.
ETH0_SYS_WAKE_TIME	0x40481060	FULL	Used to pause transmission after deassertion of tx_lpi_en. Each unit in this register corresponds to 64ns in gigabit mode, 320ns in 100M mode and 3200ns at 10M. After tx_lpi_en is deasserted transmission will pause for the set time.
ETH0_HASH_BOTTOM	0x40481080	FULL	The unicast hash enable and the multicast hash enable bits in the network configuration register enable the reception of hash matched frames. Hash Register Bottom (31 to 0 bits)
ETH0_HASH_TOP	0x40481084	FULL	Hash Register Top (63 to 32 bits)

Register Name	Address	Permission	Description
ETH0_SPEC_ADD1_BOTTOM	0x40481088	FULL	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
ETH0_SPEC_ADD1_TOP	0x4048108C	FULL	Specific Address Top
ETH0_SPEC_ADD2_BOTTOM	0x40481090	FULL	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
ETH0_SPEC_ADD2_TOP	0x40481094	FULL	Specific Address Top
ETH0_SPEC_ADD3_BOTTOM	0x40481098	FULL	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
ETH0_SPEC_ADD3_TOP	0x4048109C	FULL	Specific Address Top
ETH0_SPEC_ADD4_BOTTOM	0x404810A0	FULL	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
ETH0_SPEC_ADD4_TOP	0x404810A4	FULL	Specific Address Top
ETH0_SPEC_TYPE1	0x404810A8	FULL	Type ID Match 1
ETH0_SPEC_TYPE2	0x404810AC	FULL	Type ID Match 2
ETH0_SPEC_TYPE3	0x404810B0	FULL	Type ID Match 3
ETH0_SPEC_TYPE4	0x404810B4	FULL	Type ID Match 4
ETH0_WOL_REGISTER	0x404810B8	FULL	Wake on LAN Register. Presents in design, but feature is not supported.
ETH0_STRETCH_RATIO	0x404810BC	FULL	IPG stretch register
ETH0_STACKED_VLAN	0x404810C0	FULL	Stacked VLAN Register
ETH0_TX_PFC_PAUSE	0x404810C4	FULL	Transmit PFC Pause Register
ETH0_MASK_ADD1_BOTTOM	0x404810C8	FULL	Specific Address Mask 1 Bottom (31 to 0 bits)
ETH0_MASK_ADD1_TOP	0x404810CC	FULL	Specific Address Mask 1 Top (47 to 32 bits)
ETH0_DMA_ADDR_OR_MASK	0x404810D0	FULL	Receive DMA Data Buffer Address Mask
ETH0_RX_PTP_UNICAST	0x404810D4	FULL	PTP RX unicast IP destination address
ETH0_TX_PTP_UNICAST	0x404810D8	FULL	PTP TX unicast IP destination address
ETH0_TSU_NSEC_CMP	0x404810DC	FULL	TSU timer comparison value nanoseconds
ETH0_TSU_SEC_CMP	0x404810E0	FULL	TSU timer comparison value seconds (31 to 0 bits)
ETH0_TSU_MSB_SEC_CMP	0x404810E4	FULL	TSU timer comparison value seconds (47 to 32 bits)
ETH0_TSU_PTP_TX_MSB_SEC	0x404810E8	FULL	PTP Event Frame Transmitted Seconds Register (47 to 32 bits)
ETH0_TSU_PTP_RX_MSB_SEC	0x404810EC	FULL	PTP Event Frame Received Seconds Register (47 to 32 bits)
ETH0_TSU_PEER_TX_MSB_SEC	0x404810F0	FULL	PTP Peer Event Frame Transmitted Seconds Register (47 to 32 bits)
ETH0_TSU_PEER_RX_MSB_SEC	0x404810F4	FULL	PTP Peer Event Frame Received Seconds Register (47 to 32 bits)
ETH0_DPRAM_FILL_DBG	0x404810F8	FULL	The fill levels for the TX & RX packet buffers can be read using this register, including the fill level for each queue in the TX direction.
ETH0_REVISION_REG	0x404810FC	FULL	This register indicates a Cadence module identification number and module revision. The value of this register is read only as defined by <code>gem_revision_reg_value</code>
ETH0_OCTETS_TXED_BOTTOM	0x40481100	FULL	Octets Transmitted lower bits (31 to 0 bits)
ETH0_OCTETS_TXED_TOP	0x40481104	FULL	Octets Transmitted higher bits (47 to 32 bits)
ETH0_FRAMES_TXED_OK	0x40481108	FULL	Frames Transmitted
ETH0_BROADCAST_TXED	0x4048110C	FULL	Broadcast Frames Transmitted
ETH0_MULTICAST_TXED	0x40481110	FULL	Multicast Frames Transmitted
ETH0_PAUSE_FRAMES_TXED	0x40481114	FULL	Pause Frames Transmitted
ETH0_FRAMES_TXED_64	0x40481118	FULL	64 Byte Frames Transmitted

Register Name	Address	Permission	Description
ETH0_FRAMES_TXED_65	0x4048111C	FULL	65 to 127 Byte Frames Transmitted
ETH0_FRAMES_TXED_128	0x40481120	FULL	128 to 255 Byte Frames Transmitted
ETH0_FRAMES_TXED_256	0x40481124	FULL	256 to 511 Byte Frames Transmitted
ETH0_FRAMES_TXED_512	0x40481128	FULL	512 to 1023 Byte Frames Transmitted
ETH0_FRAMES_TXED_1024	0x4048112C	FULL	1024 to 1518 Byte Frames Transmitted
ETH0_FRAMES_TXED_1519	0x40481130	FULL	Greater Than 1518 Byte Frames Transmitted
ETH0_TX_UNDERRUNS	0x40481134	FULL	Transmit Under Runs
ETH0_SINGLE_COLLISIONS	0x40481138	FULL	Single Collision Frames. Presents in design but not support.
ETH0_MULTIPLE_COLLISIONS	0x4048113C	FULL	Multiple Collision Frames. Presents in design but not support.
ETH0_EXCESSIVE_COLLISIONS	0x40481140	FULL	Excessive Collisions. Presents in design but not support.
ETH0_LATE_COLLISIONS	0x40481144	FULL	Late Collisions. Presents in design but not support.
ETH0_DEFERRED_FRAMES	0x40481148	FULL	Deferred Transmission Frames. Presents in design but not support.
ETH0_CRS_ERRORS	0x4048114C	FULL	Carrier Sense Errors. Presents in design but not support.
ETH0_OCTETS_RXED_BOTTOM	0x40481150	FULL	Octets Received (31 to 0 bits)
ETH0_OCTETS_RXED_TOP	0x40481154	FULL	Octets Received (47 to 32 bits)
ETH0_FRAMES_RXED_OK	0x40481158	FULL	Frames Received
ETH0_BROADCAST_RXED	0x4048115C	FULL	Broadcast Frames Received
ETH0_MULTICAST_RXED	0x40481160	FULL	Multicast Frames Received
ETH0_PAUSE_FRAMES_RXED	0x40481164	FULL	Pause Frames Received
ETH0_FRAMES_RXED_64	0x40481168	FULL	64 Byte Frames Received
ETH0_FRAMES_RXED_65	0x4048116C	FULL	65 to 127 Byte Frames Received
ETH0_FRAMES_RXED_128	0x40481170	FULL	128 to 255 Byte Frames Received
ETH0_FRAMES_RXED_256	0x40481174	FULL	256 to 511 Byte Frames Received
ETH0_FRAMES_RXED_512	0x40481178	FULL	512 to 1023 Byte Frames Received
ETH0_FRAMES_RXED_1024	0x4048117C	FULL	1024 to 1518 Byte Frames Received
ETH0_FRAMES_RXED_1519	0x40481180	FULL	1519 to maximum Byte Frames Received
ETH0_UNDERSIZE_FRAMES	0x40481184	FULL	Undersized Frames Received
ETH0_EXCESSIVE_RX_LENGTH	0x40481188	FULL	Oversize Frames Received
ETH0_RX_JABBERS	0x4048118C	FULL	Jabbers Received
ETH0_FCS_ERRORS	0x40481190	FULL	Frame Check Sequence Errors
ETH0_RX_LENGTH_ERRORS	0x40481194	FULL	Length Field Frame Errors
ETH0_RX_SYMBOL_ERRORS	0x40481198	FULL	Receive Symbol Errors
ETH0_ALIGNMENT_ERRORS	0x4048119C	FULL	Alignment Errors
ETH0_RX_RESOURCE_ERRORS	0x404811A0	FULL	Receive Resource Errors
ETH0_RX_OVERRUNS	0x404811A4	FULL	Receive Overruns
ETH0_RX_IP_CHK_ERRORS	0x404811A8	FULL	IP Header Checksum Errors
ETH0_RX_TCP_CHK_ERRORS	0x404811AC	FULL	TCP Checksum Errors
ETH0_RX_UDP_CHK_ERRORS	0x404811B0	FULL	UDP Checksum Errors
ETH0_AUTO_FLUSHED_PKTS	0x404811B4	FULL	Receive DMA Flushed Packets
ETH0_TSU_TIMER_INCR_SUB_NSEC	0x404811BC	FULL	1588 Timer Increment Register sub nsec
ETH0_TSU_TIMER_MSB_SEC	0x404811C0	FULL	1588 Timer Seconds Register (47 to 32 bits)
ETH0_TSU_STROBE_MSB_SEC	0x404811C4	FULL	1588 Timer Sync Strobe Seconds Register (47 to 32 bits)
ETH0_TSU_STROBE_SEC	0x404811C8	FULL	1588 Timer Sync Strobe Seconds Register (31 to 0 bits)
ETH0_TSU_STROBE_NSEC	0x404811CC	FULL	1588 Timer Sync Strobe Nanoseconds Register
ETH0_TSU_TIMER_SEC	0x404811D0	FULL	1588 Timer Seconds Register (31 to 0 bits)
ETH0_TSU_TIMER_NSEC	0x404811D4	FULL	1588 Timer Nanoseconds Register
ETH0_TSU_TIMER_ADJUST	0x404811D8	FULL	This register is used to adjust the value of the timer in the TSU. It allows an integral number of nanoseconds to be added or subtracted from the timer in a one-off operation. This register returns all zeroes when read.
ETH0_TSU_TIMER_INCR	0x404811DC	FULL	1588 Timer Increment Register
ETH0_TSU_PTP_TX_SEC	0x404811E0	FULL	PTP Event Frame Transmitted Seconds Register (31 to 0 bits)
ETH0_TSU_PTP_TX_NSEC	0x404811E4	FULL	PTP Event Frame Transmitted Nanoseconds Register

Register Name	Address	Permission	Description
ETH0_TSU_PTP_RX_SEC	0x404811E8	FULL	PTP Event Frame Received Seconds Register (31 to 0 bits)
ETH0_TSU_PTP_RX_NSEC	0x404811EC	FULL	PTP Event Frame Received Nanoseconds Register
ETH0_TSU_PEER_TX_SEC	0x404811F0	FULL	PTP Peer Event Frame Transmitted Seconds Register (31 to 0 bits)
ETH0_TSU_PEER_TX_NSEC	0x404811F4	FULL	PTP Peer Event Frame Transmitted Nanoseconds Register
ETH0_TSU_PEER_RX_SEC	0x404811F8	FULL	PTP Peer Event Frame Received Seconds Register (31 to 0 bits)
ETH0_TSU_PEER_RX_NSEC	0x404811FC	FULL	PTP Peer Event Frame Received Nanoseconds Register
ETH0_PCS_CONTROL	0x40481200	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_STATUS	0x40481204	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_ADV	0x40481210	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_LP_BASE	0x40481214	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_EXP	0x40481218	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_NP_TX	0x4048121C	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_LP_NP	0x40481220	FULL	Not presents. Access to the register returns AHB error.
ETH0_PCS_AN_EXT_STATUS	0x4048123C	FULL	Not presents. Access to the register returns AHB error.
ETH0_TX_PAUSE_QUANTUM1	0x40481260	FULL	Transmit Pause Quantum Register 1
ETH0_TX_PAUSE_QUANTUM2	0x40481264	FULL	Transmit Pause Quantum Register 2
ETH0_TX_PAUSE_QUANTUM3	0x40481268	FULL	Transmit Pause Quantum Register 3
ETH0_RX_LPI	0x40481270	FULL	Received LPI transitions
ETH0_RX_LPI_TIME	0x40481274	FULL	Received LPI time
ETH0_TX_LPI	0x40481278	FULL	Transmit LPI transitions
ETH0_TX_LPI_TIME	0x4048127C	FULL	Transmit LPI time
ETH0_DESIGNCFG_DEBUG1	0x40481280	FULL	The GEM_GXL(3PIP) has many parameterisation options to configure the IP during compilation stage. This is achieved using Verilog define compiler directives in an include file called mxeth_defs.v.
ETH0_DESIGNCFG_DEBUG2	0x40481284	FULL	Design Configuration Register 2
ETH0_DESIGNCFG_DEBUG3	0x40481288	FULL	Design Configuration Register 3
ETH0_DESIGNCFG_DEBUG4	0x4048128C	FULL	Design Configuration Register 4
ETH0_DESIGNCFG_DEBUG5	0x40481290	FULL	Design Configuration Register 5
ETH0_DESIGNCFG_DEBUG6	0x40481294	FULL	Design Configuration Register 6
ETH0_DESIGNCFG_DEBUG7	0x40481298	FULL	Design Configuration Register 7
ETH0_DESIGNCFG_DEBUG8	0x4048129C	FULL	Design Configuration Register 8
ETH0_DESIGNCFG_DEBUG9	0x404812A0	FULL	Design Configuration Register 9
ETH0_DESIGNCFG_DEBUG10	0x404812A4	FULL	Design Configuration Register 10
ETH0_SPEC_ADD5_BOTTOM	0x40481300	FULL	Specific address registers 5 ~ 36 doesn't present. Access to the register returns AHB error.
ETH0_SPEC_ADD5_TOP	0x40481304	FULL	Specific address registers 5 ~ 36 doesn't present. Access to the register returns AHB error.
ETH0_SPEC_ADD36_BOTTOM	0x404813F8	FULL	Not presents.
ETH0_SPEC_ADD36_TOP	0x404813FC	FULL	Not presents.
ETH0_INT_Q1_STATUS	0x40481400	FULL	Priority queue Interrupt Status Register
ETH0_INT_Q2_STATUS	0x40481404	FULL	Priority queue Interrupt Status Register
ETH0_INT_Q3_STATUS	0x40481408	FULL	int_q3_status to int_q15_status doesn't present. Access to the register returns AHB error.
ETH0_INT_Q15_STATUS	0x40481438	FULL	Not presents.

Register Name	Address	Permission	Description
ETH0_TRANSMIT_Q1_PTR	0x40481440	FULL	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.
ETH0_TRANSMIT_Q2_PTR	0x40481444	FULL	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.
ETH0_TRANSMIT_Q3_PTR	0x40481448	FULL	transmit_q3_ptr to transmit_q15_ptr doesn't present. Access to the register returns AHB error.
ETH0_TRANSMIT_Q15_PTR	0x40481478	FULL	Not presents.

Register Name	Address	Permission	Description
ETH0_RECEIVE_Q1_PTR	0x40481480	FULL	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.
ETH0_RECEIVE_Q2_PTR	0x40481484	FULL	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.
ETH0_RECEIVE_Q3_PTR	0x40481488	FULL	Not presents. Start address register doesn't present for queue3 ~ queue7.
ETH0_RECEIVE_Q7_PTR	0x40481498	FULL	Not presents.
ETH0_DMA_RXBUF_SIZE_Q1	0x404814A0	FULL	Receive Buffer queue 1 Size
ETH0_DMA_RXBUF_SIZE_Q2	0x404814A4	FULL	Receive Buffer queue 2 Size
ETH0_DMA_RXBUF_SIZE_Q3	0x404814A8	FULL	dma_rxbuf_size_q3 to dma_rxbuf_size_q7 doesn't present.
ETH0_DMA_RXBUF_SIZE_Q7	0x404814B8	FULL	Not presents.

Register Name	Address	Permission	Description
ETH0_CBS_CONTROL	0x404814BC	FULL	The IdleSlope value is defined as the rate of change of credit when a packet is waiting to be sent. This must not exceed the portTransmitRate which is dependent on the speed of operation, eg, portTranmsitRate. 1Gb/s = 32'h07735940 (125 Mbytes/s), 100Mb/sec = 32'h017D7840 (25 Mnibbles/s), 10Mb/sec = 32'h002625A0 (2.5 Mnibbles/s). If 50 percent of bandwidth was to be allocated to a particular queue in 1Gb/sec mode then the IdleSlope value for that queue would be calculated as 32'h07735940/2. Note that Credit-Based Shaping should be disabled prior to updating the IdleSlope values. As another example, for a 1722 audio packet with a payload of 6 samples per channel, the packet size would be 7 (preamble) + 1 (SFD) + 50 (packet header) + 6x4x2(payload) + 4 (CRC) = 110 bytes. For a rate of 8000 packets per second, the desired rate would 110 x 8000 bytes per second, so the programmed idleSlope value would be 880000 for a 1Gb/s connection, or 1760000 for a 100Mb/s or 10Mbs connection. See Figure 6.3 in the IEEE 1722 standard. In practice, the actual transmission rate will be vary slightly from that calculated. In this case, the idleSlope value should be recalibrated based on the variance between the measured and expected rate, and in this case very accurate transmission rates can be achieved.
ETH0_CBS_IDLESLOPE_Q_A	0x404814C0	FULL	queue A is the highest priority queue. This would be queue 8 in an 8 queue configuration.
ETH0_CBS_IDLESLOPE_Q_B	0x404814C4	FULL	queue B is the 2nd highest priority queue. This would be queue 7 in an 8 queue configuration.
ETH0_UPPER_TX_Q_BASE_ADDR	0x404814C8	FULL	Upper 32 bits of transmit buffer descriptor queue base address.
ETH0_TX_BD_CONTROL	0x404814CC	FULL	TX BD control register
ETH0_RX_BD_CONTROL	0x404814D0	FULL	RX BD control register
ETH0_UPPER_RX_Q_BASE_ADDR	0x404814D4	FULL	Upper 32 bits of receive buffer descriptor queue base address.
ETH0_HIDDEN_REG0	0x404814E0	FULL	Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_10m 12'h4e0 // 10M Port TX Rate *** HIDDEN Register ***. Default value of cbs related hidden registers (0x14E0~0x14E8) are depicted in cbs_control register.
ETH0_HIDDEN_REG1	0x404814E4	FULL	Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_100m 12'h4e4 // 100M Port TX Rate *** HIDDEN Register ***
ETH0_HIDDEN_REG2	0x404814E8	FULL	Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_1g 12'h4e8 // 1G Port TX Rate *** HIDDEN Register ***
ETH0_HIDDEN_REG3	0x404814EC	FULL	Hidden registers defined in edma_defs.v ``define gem_wd_counter 12'h4ec // *** HIDDEN Register ***.

Register Name	Address	Permission	Description
ETH0_SCREENING_TYPE_1_REGISTER_0	0x40481500	FULL	Screening type 1 registers are used to allocate up to 16 priority queues to received frames based on certain IP or UDP fields of incoming frames. Firstly, when DS/TC match enable is set (bit 28), the DS (Differentiated Services) field of the received IPv4 header or TCfield (traffic class) of IPv6 headers are matched against bits 11 to 4. Secondly, when UDP port match enable is set (bit 29), the UDP Destination Port of the received UDP frame is matched against bits 27 to 12. Both UDP and DS/TC matching can be enabled simultaneously or individually. If a match is successful, then the queue value programmed in bits 2 to 0 is allocated to the frame. The required number of Type 1 screening registers is configured in the gem defines file. Up to 16 type 1 screening registers have been allocated APB address space between 0x500 and 0x53C.
ETH0_SCREENING_TYPE_1_REGISTER_1	0x40481504	FULL	screening type 1 register 1, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_2	0x40481508	FULL	screening type 1 register 2, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_3	0x4048150C	FULL	screening type 1 register 3, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_4	0x40481510	FULL	screening type 1 register 4, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_5	0x40481514	FULL	screening type 1 register 5, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_6	0x40481518	FULL	screening type 1 register 6, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_7	0x4048151C	FULL	screening type 1 register 7, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_8	0x40481520	FULL	screening type 1 register 8, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_9	0x40481524	FULL	screening type 1 register 9, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_10	0x40481528	FULL	screening type 1 register 10, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_11	0x4048152C	FULL	screening type 1 register 11, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_12	0x40481530	FULL	screening type 1 register 12, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_13	0x40481534	FULL	screening type 1 register 13, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_14	0x40481538	FULL	screening type 1 register 14, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_1_REGISTER_15	0x4048153C	FULL	screening type 1 register 15, same as screening_type_1_register_0
ETH0_SCREENING_TYPE_2_REGISTER_0	0x40481540	FULL	Screening Type 2 match registers operate independently of screening type 1 registers and offer additional match capabilities, extending the capabilities into vendor specific protocols.
ETH0_SCREENING_TYPE_2_REGISTER_1	0x40481544	FULL	screening type 2 register 1, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_2	0x40481548	FULL	screening type 2 register 2, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_3	0x4048154C	FULL	screening type 2 register 3, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_4	0x40481550	FULL	screening type 2 register 4, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_5	0x40481554	FULL	screening type 2 register 5, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_6	0x40481558	FULL	screening type 2 register 6, same as screening_type_2_register_0

Register Name	Address	Permission	Description
ETH0_SCREENING_TYPE_2_REGISTER_7	0x4048155C	FULL	screening type 2 register 7, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_8	0x40481560	FULL	screening type 2 register 8, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_9	0x40481564	FULL	screening type 2 register 9, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_10	0x40481568	FULL	screening type 2 register 10, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_11	0x4048156C	FULL	screening type 2 register 11, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_12	0x40481570	FULL	screening type 2 register 12, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_13	0x40481574	FULL	screening type 2 register 13, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_14	0x40481578	FULL	screening type 2 register 14, same as screening_type_2_register_0
ETH0_SCREENING_TYPE_2_REGISTER_15	0x4048157C	FULL	screening type 2 register 15, same as screening_type_2_register_0
ETH0_TX_SCHED_CTRL	0x40481580	FULL	This register controls the transmit scheduling algorithm the user can select for each active transmit queue. By default all queues are initialized to fixed priority, with the top indexed queue having overall priority
ETH0_BW_RATE_LIMIT_Q0TO3	0x40481590	FULL	This register holds the DWRR weighting value or the ETS bandwidth percentage value used by the transmit scheduler for queues 0 to 3.
ETH0_BW_RATE_LIMIT_Q4TO7	0x40481594	FULL	Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
ETH0_BW_RATE_LIMIT_Q8TO11	0x40481598	FULL	Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
ETH0_BW_RATE_LIMIT_Q12TO15	0x4048159C	FULL	Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
ETH0_TX_Q_SEG_ALLOC_Q0TO7	0x404815A0	FULL	This register allows the user to distribute the Transmit SRAM used by the DMA across the priority queues, for queues 0 to 7. The SRAM itself is split into a number of evenly sized segments (this is defined in the verilog configuration defs file - for the configuration used to generate this register description, the total number of segments was set to '16'). Those segments can then be freely distributed across the active queues, in powers of 2. I.e. a value of 0 would mean 1 segment has been allocated to the queue. A value of 1 would mean 2 segments, a value of 2 means 4 segments and so on. The reset values of these registers are defined in the configuration defs file.
ETH0_TX_Q_SEG_ALLOC_Q8TO15	0x404815A4	FULL	Not presents. Access to the register returns AHB error.
ETH0_RECEIVE_Q8_PTR	0x404815C0	FULL	receive_q8_ptr to receive_q15_ptr doesn't present. Access to the register returns AHB error.
ETH0_RECEIVE_Q15_PTR	0x404815DC	FULL	Not presents.
ETH0_DMA_RXBUF_SIZE_Q8	0x404815E0	FULL	dma_rxbuf_size_q8 to dma_rxbuf_size_q15 doesn't present. Access to the register returns AHB error.
ETH0_DMA_RXBUF_SIZE_Q15	0x404815FC	FULL	Not presents.
ETH0_INT_Q1_ENABLE	0x40481600	FULL	At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.
ETH0_INT_Q2_ENABLE	0x40481604	FULL	At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.

Register Name	Address	Permission	Description
ETH0_INT_Q3_ENABLE	0x40481608	FULL	int_q3_enable to int_q7_enable doesn't present. Access to the register returns AHB error.
ETH0_INT_Q7_ENABLE	0x40481618	FULL	Not presents.
ETH0_INT_Q1_DISABLE	0x40481620	FULL	Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.
ETH0_INT_Q2_DISABLE	0x40481624	FULL	Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.
ETH0_INT_Q3_DISABLE	0x40481628	FULL	int_q3_disable to int_q7_disable doesn't present. Access to the register returns AHB error.
ETH0_INT_Q7_DISABLE	0x40481638	FULL	Not presents.
ETH0_INT_Q1_MASK	0x40481640	FULL	The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.
ETH0_INT_Q2_MASK	0x40481644	FULL	The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.
ETH0_INT_Q3_MASK	0x40481648	FULL	int_q3_mask to int_q7_mask doesn't present. Access to the register returns AHB error.
ETH0_INT_Q7_MASK	0x40481658	FULL	Not presents.
ETH0_INT_Q8_ENABLE	0x40481660	FULL	int_q8_enable to int_q15_enable doesn't present. Access to the register returns AHB error.
ETH0_INT_Q15_ENABLE	0x4048167C	FULL	Not presents.
ETH0_INT_Q8_DISABLE	0x40481680	FULL	int_q8_disable to int_q15_disable doesn't present. Access to the register returns AHB error.
ETH0_INT_Q15_DISABLE	0x4048169C	FULL	Not presents.
ETH0_INT_Q8_MASK	0x404816A0	FULL	int_q8_mask to int_q15_mask doesn't present. Access to the register returns AHB error.
ETH0_INT_Q15_MASK	0x404816BC	FULL	Not presents.
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_0	0x404816E0	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_1	0x404816E4	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_2	0x404816E8	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_3	0x404816EC	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_4	0x404816F0	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_5	0x404816F4	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_6	0x404816F8	FULL	Ethertype Register
ETH0_SCREENING_TYPE_2_ETHERTYPE_REG_7	0x404816FC	FULL	Ethertype Register

Register Name	Address	Permission	Description
ETH0_TYPE2_COMPARE_0_WORD_0	0x40481700	FULL	'Compare A, B and C fields of the screener type 2 match register are pointers to a pool of up to 32 compare registers. If enabled the compare is true if the data at the OFFSET into the frame, ANDed with the MASK Value if the mask is enabled, is equal to the COMPARE Value. Either a 16 bit comparison or a 32 bit comparison is done. This selection is made via the associated compare word1 register bit 9. If a 16 bit comparison is selected, then a 16 bit mask is also available to the user to select which bits should be compared. If the 32 bit compare option is selected, then no mask is available. The byte at the OFFSET number of bytes from the index start is compared thru bits 7 to 0 of the configured VALUE. The byte at the OFFSET number of bytes + 1 from the index start is compared thru bits 15 to 8 of the configured VALUE and so on. The OFFSET can be configured to be from 0 to 127 bytes from either the start of the frame, the byte following the therType field (last EtherType in the header if the frame is VLAN tagged), the byte following the IP header (IPv4 or IPv6) or from the byte following the start of the TCP/UDP header. The required number of Type 2 screening registers up to a maximum of 32 is configurable in the gem defines file and have been allocated APB address space between 0x700 and 0x7fc. Note. when using RX Partial Store and Forward mode and priority queues, the frame offset must be less than the Partial Store and Forward watermark. If the offset is higher than the watermark value it's not possible to identify the priority queue before the frame is sent to the AMBA interface, and an incorrect priority queue may be used.'
ETH0_TYPE2_COMPARE_0_WORD_1	0x40481704	FULL	'Type2 Compare Word 1'
ETH0_TYPE2_COMPARE_1_WORD_0	0x40481708	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_1_WORD_1	0x4048170C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_2_WORD_0	0x40481710	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_2_WORD_1	0x40481714	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_3_WORD_0	0x40481718	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_3_WORD_1	0x4048171C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_4_WORD_0	0x40481720	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_4_WORD_1	0x40481724	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_5_WORD_0	0x40481728	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_5_WORD_1	0x4048172C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_6_WORD_0	0x40481730	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_6_WORD_1	0x40481734	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_7_WORD_0	0x40481738	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_7_WORD_1	0x4048173C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_8_WORD_0	0x40481740	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_8_WORD_1	0x40481744	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_9_WORD_0	0x40481748	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_9_WORD_1	0x4048174C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_10_WORD_0	0x40481750	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_10_WORD_1	0x40481754	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_11_WORD_0	0x40481758	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_11_WORD_1	0x4048175C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_12_WORD_0	0x40481760	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_12_WORD_1	0x40481764	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_13_WORD_0	0x40481768	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_13_WORD_1	0x4048176C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_14_WORD_0	0x40481770	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_14_WORD_1	0x40481774	FULL	same as type2_compare_0_word_1

Register Name	Address	Permission	Description
ETH0_TYPE2_COMPARE_15_WORD_0	0x40481778	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_15_WORD_1	0x4048177C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_16_WORD_0	0x40481780	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_16_WORD_1	0x40481784	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_17_WORD_0	0x40481788	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_17_WORD_1	0x4048178C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_18_WORD_0	0x40481790	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_18_WORD_1	0x40481794	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_19_WORD_0	0x40481798	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_19_WORD_1	0x4048179C	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_20_WORD_0	0x404817A0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_20_WORD_1	0x404817A4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_21_WORD_0	0x404817A8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_21_WORD_1	0x404817AC	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_22_WORD_0	0x404817B0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_22_WORD_1	0x404817B4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_23_WORD_0	0x404817B8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_23_WORD_1	0x404817BC	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_24_WORD_0	0x404817C0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_24_WORD_1	0x404817C4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_25_WORD_0	0x404817C8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_25_WORD_1	0x404817CC	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_26_WORD_0	0x404817D0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_26_WORD_1	0x404817D4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_27_WORD_0	0x404817D8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_27_WORD_1	0x404817DC	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_28_WORD_0	0x404817E0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_28_WORD_1	0x404817E4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_29_WORD_0	0x404817E8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_29_WORD_1	0x404817EC	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_30_WORD_0	0x404817F0	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_30_WORD_1	0x404817F4	FULL	same as type2_compare_0_word_1
ETH0_TYPE2_COMPARE_31_WORD_0	0x404817F8	FULL	same as type2_compare_0_word_0
ETH0_TYPE2_COMPARE_31_WORD_1	0x404817FC	FULL	same as type2_compare_0_word_1

11.1 Register Details

11.1.1 ETH_CTL

Description: MXETH Control Register
Address: 0x40480000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: The field ETH_MODE and REFCLK_SRC will select clock source for MAC transmit and receive logic in different Eth mode, it should NOT be changed while ENABLED is '1'.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					REFCLK_SRC_SEL [2:2]	ETH_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	REFCLK_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	ETH_MODE	RW	RW	0	Set ethernet mode. The speed of 10M/100M/1G is selected by programming network_config after IP is enabled. The field also specifies the clock source of internal tx_clk and rx_clk domain.
	MII			0	MII mode (10/100MHz speed is determined by network_config[0]).
	GMII			1	GMII mode (network_config[10] must be set to enable 1G operation).
	RGMII			2	RGMII mode (10M/100M/1G speed is determined by network_config[10] and network_config[0]).
	RMII			3	RMII mode (10M/100M speed is determined by network_config[0]).
2	REFCLK_SRC_SEL	RW	RW	0	Select the source for ref_clk. 0: Ref_clk comes from REF_CLK_IN input port (HSIO). 1: Ref_clk comes from REF_CLK_INT_IN input port (PLL).
8:15	REFCLK_DIV	RW	RW	0	Specify the ref_clk divider. Integer division by (1+REFCLK_DIV). Allows for integer divisions in the range [1, 256].
31	ENABLED	RW	RW	0	MXETH enable: '0': Disabled. '1': Enabled.

11.1.2 ETH_STATUS

Description: MXETH Status Register
Address: 0x40480004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							PFC_NEGOTIATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	RX_PFC_PAUSED [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PFC_NEGOTIATE	R	R	0	Identifies that PFC priority based pause flow control has been negotiated. 0 - No PFC priority based pause frames have yet been received, flow control is being handled using classic 802.3 pause frames. 1 - At least one PFC priority based pause frames has been received. All subsequent 802.3 pause frames will be dropped.
8:15	RX_PFC_PAUSED	R	R	0	Each bit corresponds to a priority indicated within the PFC priority based pause frame. Each bit is set when a PFC priority based pause frame has been received, and the associated priority pause time quantum is non-zero. Each bit is cleared when the associated pause time identified by the received pause time quantum has elapsed.

11.1.3 ETH_NETWORK_CONTROL

Description:	The network control register contains general MAC control functions for both receiver and transmitter.
Address:	0x40481000
Offset:	0x1000
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STATS_WRITE_EN [7:7]	INC_ALL_STATS_REGS [6:6]	CLEAR_ALL_STATS_REGS [5:5]	MAN_PORT_EN [4:4]	ENABLE_TRANSMIT [3:3]	ENABLE_RECEIVE [2:2]	LOOPBACK_LOCAL [1:1]	LOOPBACK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	STORE_RX_TS [15:15]	REMOVED_14 [14:14]	REMOVED_13 [13:13]	TX_PAUSE_FRAME_ZERO [12:12]	TX_PAUSE_FRAME_REQ [11:11]	TX_HALT_PCLK [10:10]	TX_START_PCLK [9:9]	BACK_PRESURE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	EXT_TSU_PORT_ENABLE [23:23]	STORE_UDP_OFFSET [22:22]	ALT_SGMII_MODE [21:21]	PTP_UNICAST_ENA [20:20]	TX_LPI_EN [19:19]	FLUSH_RX_PKT_PCLK [18:18]	TRANSMIT_PFC_PRIORITY_BASED_PAUSE_FRAME [17:17]	PFC_ENABLE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	EXT_RXQ_RESERVED_31 [31:31]	IFG_EATS_QAV_CREDIT [30:30]	TWO_PT_FIVE_GIG [29:29]	SEL_MII_ON_RGMII [28:28]	OSS_CORRECTION_FIELD [27:27]	EXT_RXQ_SEL_EN [26:26]	PFC_CTRL [25:25]	ONE_STEP_SYNC_MODE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOOPBACK	RW	RW	0	Loopback - controls the loopback output pin.
1	LOOPBACK_LOCAL	RW	RW	0	Loopback local - asserts the loopback_local signal to the system clock generator. Also connects txd to rxd, tx_en to rx_dv and forces full duplex mode. Bit 11 of the network configuration register must be set low to disable TBI mode when in internal loopback. rx_clk and tx_clk may malfunction as the GEM is switched into and out of internal loopback. It is important that receive and transmit circuits have already been disabled when making the switch into and out of internal loopback. Local loopback functionality is optional and may not be supported by some instantiations of the GEM.
2	ENABLE_RECEIVE	RW	RW	0	Receive enable - when set, it enables the GEM to receive data. When reset frame reception will stop immediately and the receive pipeline will be cleared. The receive queue pointer register is unaffected.

Bits	Name	SW	HW	Default or Enum	Description
3	ENABLE_TRANSMIT	RW	RW	0	Transmit enable - when set, it enables the GEM transmitter to send data. When reset transmission will stop immediately, the transmit pipeline and control registers will be cleared and the transmit queue pointer register will reset to point to the start of the transmit descriptor list.
4	MAN_PORT_EN	RW	RW	0	Management port enable - set to one to enable the management port. When zero forces mdio to high impedance state and mdc low.
5	CLEAR_ALL_STATS_REGS	W	W	0	Clear statistics registers - this bit is write only. Writing a one clears the statistics registers. Self clearing register.
6	INC_ALL_STATS_REGS	W	W	0	Incremental statistics registers - this bit is write only. Writing a one increments all the statistics registers by one for test purposes. Self clearing register.
7	STATS_WRITE_EN	RW	RW	0	Write enable for statistics registers - setting this bit to one means the statistics registers can be written for functional test purposes.
8	BACK_PRESSURE	RW	RW	0	Back pressure if set in 10M or 100M half duplex mode will force collisions on all received frames. Ignored in gigabit half duplex mode.
9	TX_START_PCLK	W	W	0	Start transmission - writing one to this bit starts transmission.
10	TX_HALT_PCLK	W	W	0	Transmit halt - writing one to this bit halts transmission as soon as any ongoing frame transmission ends.
11	TX_PAUSE_FRAME_REQ	W	W	0	Transmit pause frame - writing one to this bit causes a pause frame to be transmitted. Self clearing register.
12	TX_PAUSE_FRAME_ZERO	W	W	0	Transmit zero quantum pause frame - writing one to this bit causes a pause frame with zero quantum to be transmitted.
13	REMOVED_13	R	R	0	Write ignore, read 0
14	REMOVED_14	R	R	0	Write ignore, read 0
15	STORE_RX_TS	RW	RW	0	Store receive time stamp to memory. Setting this bit to one will cause the CRC of every received frame to be replaced with the value of the nanoseconds field of the 1588 timer that was captured as the receive frame passed the message time stamp point. Set to zero for normal operation.
16	PFC_ENABLE	RW	RW	0	Enable PFC Priority Based Pause Reception capabilities. Setting this bit will enable PFC negotiation and recognition of priority based pause frames.
17	TRANSMIT_PFC_PRIORITY_BASED_PAUSE_FRAME	W	W	0	Write a one to transmit PFC priority based pause frame. Takes the values stored in the Transmit PFC Pause Register. Self clearing register.
18	FLUSH_RX_PKT_PCLK	W	W	0	Flush the next packet from the external RX DPRAM. Writing one to this bit will only have an effect if the DMA is not currently writing a packet already stored in the DPRAM to memory. Self clearing register.
19	TX_LPI_EN	RW	RW	0	Enable LPI transmission when set LPI (low power idle) is immediately transmitted. LPI is transmitted even if bit 3 transmit enable is disabled. Setting this bit also sends a pause signal to the transmit datapath.
20	PTP_UNICAST_ENA	RW	RW	0	Enable detection of unicast PTP unicast frames.
21	ALT_SGMII_MODE	RW	RW	0	Alternative sgmmii mode. If asserted with sgmmii_mode in the network control register the ACK bit is driven before ability detect during transfer of status information from the PHY to the MAC.

Bits	Name	SW	HW	Default or Enum	Description
22	STORE_UDP_OFFSET	RW	RW	0	Store UDP / TCP offset to memory. Setting this bit to one will cause the upper 16-bits of the CRC of every received frame to be replaced with the offset from start of frame to the beginning of the UDP or TCP header. The lower 16-bits of the CRC are replaced with zero and reserved for future use. The offset is measured in units of 2 bytes. Set to zero for normal operation.
23	EXT_TSU_PORT_ENABLE	R	R	0	Write ignore, read 0
24	ONE_STEP_SYNC_MODE	RW	RW	0	1588 One Step Sync Mode. Write 1 to enable. Replace timestamp field in the 1588 header for TX Sync Frames with current TSU timer value.
25	PFC_CTRL	RW	RW	0	'Enable multiple PFC pause quanta, one per pause priority'
26	EXT_RXQ_SEL_EN	RW	RW	0	Enable external selection of receive queue. When this bit is high the ext_match1, ext_match2, ext_match3 and ext_match4 inputs will determine which receive queue a frame is routed to. This will be the case regardless of the state of the external address match enable bit 9 of the network config register. Note that receive frames will be dropped unless they are matched by the internal frame filtering functionality. If the external address match enable bit 9 in the network config register is set frames may be matched by an external address match filter as long as one of the ext_match1, ext_match2, ext_match3 and ext_match4 inputs is asserted early enough. When set ext_rxq_sel_en takes precedence over the existing screener functionality. This bit is only relevant if priority queuing is configured.
27	OSS_CORRECTION_FIELD	RW	RW	0	1588 One Step Correction Field Update. Set this bit high to enable updating the correction field of PTP 1588 version 2 sync frames by adding current TSU timer value.
28	SEL_MII_ON_RGMII	RW	RW	0	If the RGMII interface being used set this bit high to configure the interface for MII operation.
29	TWO_PT_FIVE_GIG	RW	RW	0	2.5G operation selected - setting this bit high drives the speed_mode[3] top level output pin high and also adjusts the link timer in the PCS auto-negotiation block to ensure it delivers 10ms for 2500BASE-X and 1.6ms in SGMII mode, and also ensures int_moderation counts 800ns periods with the speeded up MAC clocks.
30	IFG_EATS_QAV_CREDIT	RW	RW	0	Setting this bit high modifies the CBS algorithm so the IFG/IPG associated with a transmit frame counts towards its 802.1Qav credit.
31	EXT_RXQ_RESERVED_31	R	R	0	Reserved, read as 0, ignored on write.

11.1.4 ETH_NETWORK_CONFIG

Description:	The network configuration register contains functions for setting the mode of operation for the Gigabit Ethernet MAC.
Address:	0x40481004
Offset:	0x1004
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x2C0000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UNICAST_HASH_ENABLE [7:7]	MULTICAST_HASH_ENABLE [6:6]	NO_BROADCAST [5:5]	COPY_ALL_FRAMES [4:4]	JUMBO_FRAMES [3:3]	DISCARD_NON_VLAN_FRAMES [2:2]	FULL_DUPLEX [1:1]	SPEED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	RECEIVE_BUFFER_OFFSET [15:14]		PAUSE_ENABLE [13:13]	RETRY_TEST [12:12]	PCS_SELECT [11:11]	GIGABIT_MODE_ENABLE [10:10]	EXTERNAL_ADDRESS_MATCH_ENABLE [9:9]	RECEIVE_1536_BYTE_FRAMES [8:8]

Bits	23	22	21	20	19	18	17	16
Name	DISABLE_COPY_OF_PAUSE_FRAMES [23:23]	DATA_BUS_WIDTH [22:21]		MDC_CLOCK_DIVISION [20:18]			FCS_REMOVE [17:17]	LENGTH_FIELD_ERROR_FRAME_DISCARD [16:16]

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	IGNORE_IP_RX_ERROR [30:30]	NSP_CHANGE [29:29]	IPG_STRETCH_ENABLE [28:28]	SGMII_MODE_ENABLE [27:27]	IGNORE_RX_FCS [26:26]	EN_HALF_DUPLEX_RX [25:25]	RECEIVE_CHECKSUM_OFFLOAD_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SPEED	RW	RW	0	Speed - set to logic one to indicate 100Mbps operation, logic zero for 10Mbps.
1	FULL_DUPLEX	RW	RW	0	Full duplex - if set to logic one, the transmit block ignores the state of collision and carrier sense and allows receive while transmitting. Also controls the half_duplex pin.
2	DISCARD_NON_VLAN_FRAMES	RW	RW	0	Discard non-VLAN frames - when set only VLAN tagged frames will be passed to the address matching logic.
3	JUMBO_FRAMES	RW	RW	0	Jumbo frames - set to one to enable jumbo frames up to `gem_jumbo_max_length` bytes to be accepted. The default length is 10,240 bytes.
4	COPY_ALL_FRAMES	RW	RW	0	Copy all frames - when set to logic one, all valid frames will be accepted.
5	NO_BROADCAST	RW	RW	0	No broadcast - when set to logic one, frames addressed to the broadcast address of all ones will not be accepted.

Bits	Name	SW	HW	Default or Enum	Description
6	MULTICAST_HASH_ENABLE	RW	RW	0	Multicast hash enable - when set, multicast frames will be accepted when the 6 bit hash function of the destination address points to a bit that is set in the hash register.
7	UNICAST_HASH_ENABLE	RW	RW	0	Unicast hash enable - when set, unicast frames will be accepted when the 6 bit hash function of the destination address points to a bit that is set in the hash register.
8	RECEIVE_1536_BYTE_FRAMES	RW	RW	0	Receive 1536 byte frames - setting this bit means the GEM will accept frames up to 1536 bytes in length. Normally the GEM would reject any frame above 1518 bytes.
9	EXTERNAL_ADDRESS_MATCH_ENABLE	RW	RW	0	External address match enable - when set the external address match interface can be used to copy frames to memory.
10	GIGABIT_MODE_ENABLE	RW	RW	0	Gigabit mode enable - setting this bit configures the GEM for 1000 Mbps operation. 0: 10/100 operation using MII interface 1: Gigabit operation using GMI interface
11	PCS_SELECT	RW	RW	0	PCS select - selects between MII/GMII and TBI
12	RETRY_TEST	RW	RW	0	Retry test - must be set to zero for normal operation. If set to one the backoff between collisions will always be one slot time. Setting this bit to one helps test the too many retries condition. Also used in the pause frame tests to reduce the pause counter's decrement time from 512 bit times, to every rx_clk cycle.
13	PAUSE_ENABLE	RW	RW	0	Pause enable - when set, transmission will pause if a non zero 802.3 classic pause frame is received and PFC has not been negotiated.
14:15	RECEIVE_BUFFER_OFFSET	RW	RW	0	Receive buffer offset - indicates the number of bytes by which the received data is offset from the start of the receive buffer.
16	LENGTH_FIELD_ERROR_FRAME_DISCARD	RW	RW	0	Length field error frame discard - setting this bit causes frames with a measured length shorter than the extracted length field (as indicated by bytes 13 and 14 in a non-VLAN tagged frame) to be discarded. This only applies to frames with a length field less than 0x0600.
17	FCS_REMOVE	RW	RW	0	FCS remove - setting this bit will cause received frames to be written to memory without their frame check sequence (last 4 bytes). The frame length indicated will be reduced by four bytes in this mode.
18:20	MDC_CLOCK_DIVISION	RW	RW	3	MDC clock division - set according to pclk speed. These three bits determine the number pclk will be divided by to generate MDC. For conformance with the 802.3 specification, MDC must not exceed 2.5 MHz (MDC is only active during MDIO read and write operations). The reset value for this can be changed by defining a new value for gem_mdc_clock_div in gem_defs.v 000: divide pclk by 8 (pclk up to 20 MHz) 001: divide pclk by 16 (pclk up to 40 MHz) 010: divide pclk by 32 (pclk up to 80 MHz) 011: divide pclk by 48 (pclk up to 120MHz) 100: divide pclk by 64 (pclk up to 160 MHz) 101: divide pclk by 96 (pclk up to 240 MHz) 110: divide pclk by 128 (pclk up to 320 MHz) 111: divide pclk by 224 (pclk up to 540 MHz). Note. The reset value of this field is equal to the gem_mdc_clock_div define, which is user configurable.

Bits	Name	SW	HW	Default or Enum	Description
21:22	DATA_BUS_WIDTH	RW	RW	1	Data bus width - set according to AMBA (AXI/AHB) or external FIFO data bus width. The reset value for this can be changed by defining a new value for <code>gem_dma_bus_width_def</code> in <code>gem_defs</code> . Only valid bus widths may be written if the system is configured to a maximum width less than 128-bits. 00: 32 bit data bus width 01: 64 bit AMBA (AXI/AHB) data bus width 10: 128 bit AMBA (AXI/AHB) data bus width 11: 128 bit AMBA (AXI/AHB) data bus width. Note. The reset value of this field is equal to the <code>gem_dma_bus_width_def</code> define, which is user configurable. Note: For <code>AXI_MASTER_PRESENT=1</code> , MXETH only supports 64b DMA data bus width, so must set it 1. For <code>AXI_MASTER_PRESENT=0</code> , MXETH only supports 32b DMA data bus width, so must set it 0.
23	DISABLE_COPY_OF_PAUSE_FRAMES	RW	RW	0	Disable copy of pause frames - set to one to prevent pause frames being copied to memory. When set, neither control frames with type id 8808, nor pause frames with destination address 010000c28001 are copied to memory, this functionality was enhanced in release 1p09 (mxeth uses 1p09). Note that valid pause frames received will still increment pause statistics and pause the transmission of frames as required.
24	RECEIVE_CHECKSUM_OFFLOAD_ENABLE	RW	RW	0	Receive checksum offload enable - when set, the receive checksum engine is enabled. Frames with bad IP, TCP or UDP checksums are discarded.
25	EN_HALF_DUPLEX_RX	RW	RW	0	Enable frames to be received in half-duplex mode while transmitting. Must set '0', MXETH only supports full-duplex mode.
26	IGNORE_RX_FCS	RW	RW	0	Ignore RX FCS - when set frames with FCS/CRC errors will not be rejected. FCS error statistics will still be collected for frames with bad FCS and FCS status will be recorded in frame's DMA descriptor. For normal operation this bit must be set to zero.
27	SGMII_MODE_ENABLE	RW	RW	0	SGMII mode enable - changes behaviour of the auto-negotiation advertisement and link partner ability registers to meet the requirements of SGMII and reduces the duration of the link timer from 10 ms to 1.6 ms.
28	IPG_STRETCH_ENABLE	RW	RW	0	IPG stretch enable - when set the transmit IPG can be increased above 96 bit times depending on the previous frame length using the IPG stretch register.
29	NSP_CHANGE	RW	RW	0	Receive bad preamble. When set frames with non-standard preamble are not rejected.
30	IGNORE_IPG_RX_ER	RW	RW	0	Ignore IPG rx_er. When set rx_er has no effect on the GEMs operation when rx_dv is low. Set this when using the RGMII wrapper in half-duplex mode.
31	RESERVED_31	RW	RW	0	Reserved. Writeable register. Ignore on read.

11.1.5 ETH_NETWORK_STATUS

Description:	The network status register returns status information with respect to the PHY management interface.
Address:	0x40481008
Offset:	0x1008
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LPI_INDICATE_PCLK [7:7]	PFC_NEGOTIATE_PCLK [6:6]	REMOVED_5_4 [5:4]		MAC_FULL_DUPLEX [3:3]	MAN_DONE [2:2]	MDIO_IN [1:1]	PCS_LINK_STATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PCS_LINK_STATE	R	R	0	Returns status of PCS link state. If auto-negotiation is disabled this returns the synchronisation status. If auto-negotiation is enabled it is set in the LINK_OK state as long as a compatible duplex mode is resolved.
1	MDIO_IN	R	R	1	Returns status of the mdio_in pin.
2	MAN_DONE	R	R	1	The PHY management logic is idle (i.e. has completed).
3	MAC_FULL_DUPLEX	R	R	0	PCS auto-negotiation duplex resolution. Set to one if the resolution function determines that both devices are capable of full duplex operation. If zero half-duplex operation is possible as long as bit 0 (PCS link state) is also one.
4:5	REMOVED_5_4	R	R	0	Reserved, read as 0, ignored on write.
6	PFC_NEGOTIATE_PCLK	R	R	0	Set when PFC Priority Based Pause has been negotiated.
7	LPI_INDICATE_PCLK	R	R	0	LPI Indication - Low power idle has been detected on receive. This bit is set when LPI is detected and reset when normal idle is detected. An interrupt is generated when the state of this bit changes.

11.1.6 ETH_USER_IO_REGISTER

Description: Not presents. Access to the register will return AHB error.
Address: 0x4048100C
Offset: 0x100C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Write ignore, read 0

11.1.7 ETH_DMA_CONFIG

Description: DMA Configuration Register
Address: 0x40481010
Offset: 0x1010
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x180704

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ENDIAN_SWAP_PACKET [7:7]	ENDIAN_SWAP_MANAGEMENT [6:6]	HDR_DATA_SPLITTING_EN [5:5]	AMBA_BURST_LENGTH [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		CRC_ERROR_REPORT [13:13]	INFINITE_LAST_DBUF_SIZE_EN [12:12]	TX_PBUF_TCP_EN [11:11]	TX_PBUF_SIZE [10:10]	RX_PBUF_SIZE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	RX_BUF_SIZE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	DMA_ADDR_BUS_WIDTH_1 [30:30]	TX_BD_EXT_ENDED_MODE_EN [29:29]	RX_BD_EXT_ENDED_MODE_EN [28:28]	None [27:27]	FORCE_MAX_AMBA_BURST_TX [26:26]	FORCE_MAX_AMBA_BURST_RX [25:25]	FORCE_DISCARD_ON_ERR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	AMBA_BURST_LENGTH	RW	RW	4	Selects the burst length to use on the AMBA (AHB/AXI) when transferring frame data. Not used for DMA management operations and only used where space and data size allow and respecting AXI/AHB burst boundary rules. One-hot priority encoding enforced automatically on register writes as follows, where x represents don't care: 1xxx: Attempt to use bursts of up to 16. 01xxx: Attempt to use bursts of up to 8. 001xx: Attempt to use bursts of up to 4. 0001x: Always use SINGLE bursts. 00001: Always use SINGLE bursts. 00000: Attempt to use bursts of up to 256. Note: MXETH only supports burst length up to 16.

Bits	Name	SW	HW	Default or Enum	Description
5	HDR_DATA_SPLITTING_EN	RW	RW	0	Enable header data Splitting. When set, receive frames will be forwarded to main memory using a minimum of two DMA data buffers. The first X data buffers will contain the frame header, consisting of the Ethernet, VLAN, (IPv4 or IPv6), (TCP or UDP). X= (frame header size divided by rx_buf_size as defined in bits 23:16 of this register). The last Y data buffers will contain the frame payload. Y= (frame payload size divided by rx_buf_size). Note that for non VLAN/IP/TCP/UDP frames, the header will always be 14 bytes. When this feature is disabled, the frame is forwarded to main memory in blocks of rx_buf_size. Note: For AXI_MASTER_PRESENT=0 i.e. AHB master support, this feature cannot be set.
6	ENDIAN_SWAP_MANAGEMENT	RW	RW	0	endian swap mode enable for management descriptor accesses. When set, selects swapped endianism for AMBA (AXI/AHB) transfers. When clear, selects little endian mode. Note, the default value of this bit equals to `gem_endian_swap_def, which is design time configuration.
7	ENDIAN_SWAP_PACKET	RW	RW	0	endian swap mode enable for packet data accesses. When set, selects swapped endianism for AMBA (AXI/AHB) transfers. When clear, selects little endian mode. Note, the default value of this bit equals to `gem_endian_swap_def, which is design time configuration.
8:9	RX_PBUF_SIZE	RW	RW	3	Receiver packet buffer memory size select. Having these bits at less than 11 reduces the amount of memory used for the receive packet buffer. This reduces the amount of memory used by the GEM. It is important to set these bits both to one if the full configured physical memory is available. The value in brackets below represents the size that would result for the default maximum configured memory size of 8 Kbytes. 11: Use full configured addressable space (8 Kb) 10: Do not use top address bit (4 Kb) 01: Do not use top two address bits (2 Kb) 00: Do not use top three address bits (1 Kb) If the GEM is not configured to use the DMA packet buffer, these bits are not implemented and will be treated as reserved, read as 0, ignored on write. Note. The reset value of this field is equal to the gem_rx_pbuf_size_def define, which is user configurable.
10	TX_PBUF_SIZE	RW	RW	1	Transmitter packet buffer memory size select. Having this bit at zero halves the amount of memory used for the transmit packet buffer. This reduces the amount of memory used by the GEM. It is important to set this bit to one if the full configured physical memory is available. The value in brackets below represents the size that would result for the default maximum configured memory size of 4 Kbytes. 1: Use full configured addressable space (4 Kb) 0: Do not use top address bit (2 Kb) If the GEM is not configured to use the DMA packet buffer, this bit is not implemented and will be treated as reserved, read as 0, ignored on write. Note. The reset value of this field is equal to the gem_tx_pbuf_size_def define, which is user configurable.

Bits	Name	SW	HW	Default or Enum	Description
11	TX_PBUF_TCP_EN	RW	RW	0	Transmitter IP, TCP and UDP checksum generation offload enable (not supported when in TX Partial Store and Forward mode). When set, the transmitter checksum generation engine is enabled, to calculate and substitute checksums for transmit frames. When clear, frame data is unaffected. If the GEM is not configured to use the DMA packet buffer, this bit is not implemented and will be treated as reserved, read as 0, ignored on write.
12	INFINITE_LAST_DBUF_SIZE_EN	RW	RW	0	Forces the DMA to consider the data buffer pointed to by last descriptor in the descriptor list to be of infinite size.
13	CRC_ERROR_REPORT	RW	RW	0	When the bit is set, bit 16 of the receive buffer descriptor will represent FCS/CRC error (only if frames with FCS are copied to memory as enabled by bit 26 in the network config register). When this bit is clear, bit 16 of the receive buffer descriptor will represent the Canonical format indicator (CFI) bit as extracted from the receive frame (if the receive buffer descriptor is pointing to the last data buffer of the receive frame and the received frame was VLAN tagged).
16:23	RX_BUF_SIZE	RW	RW	24	DMA receive buffer size in external AMBA (AXI/AHB) system memory. The value defined by these bits determines the size of buffer to use in main system memory when writing received data. The value is defined in multiples of 64 bytes. 0x01 corresponds to buffers of 64 bytes 0x02 corresponds to 128 bytes etc. For example: 0x02: 128 byte. 0x18: 1536 byte (1*max length frame/buffer) 0xA0: 10240 byte (1*10K jumbo frame/buffer) Note that this value should never be written as zero. Note. The reset value of this field is equal to the gem_rx_buffer_length_def define, which is user configurable.
24	FORCE_DISCARD_ON_ERR	RW	RW	0	Auto Discard RX pkts during lack of resource. When set, the GEM DMA will automatically discard receive packets from the receiver packet buffer memory when no AMBA (AXI/AHB) resource is available. When low, then received packets will remain to be stored in the SRAM based packet buffer until AMBA (AXI/AHB) buffer resource next becomes available. A write to this bit is ignored if the DMA is not configured in the packet buffer full store and forward mode.
25	FORCE_MAX_AMBA_BURST_RX	RW	RW	0	Force max length bursts on RX. Force the RX DMA to always issue max length bursts on EOP(end of packet) or EOB(end of buffer)transfers, even if there is less than max burst real packet data required to write. Any extra bytes of pad data is set to 0x00. Does not apply on bursts that break 1k boundary rule.
26	FORCE_MAX_AMBA_BURST_TX	RW	RW	0	Force max length bursts on TX. Force the TX DMA to always issue max length bursts on EOP(end of packet) or EOB(end of buffer) transfers as defined by bits 4:0 of this register, even when there is less than max burst data bytes to read. Residual data read is ignored. Does not apply on bursts that break 1k boundary rule.
28	RX_BD_EXTENDED_MODE_EN	RW	RW	0	Enable RX extended BD mode. See RX BD control register definition for description of feature.
29	TX_BD_EXTENDED_MODE_EN	RW	RW	0	Enable TX extended BD mode. See TX BD control register definition for description of feature.

Bits	Name	SW	HW	Default or Enum	Description
30	DMA_ADDR_BUS_WIDTH_1	RW	RW	0	DMA address bus width. 0 = 32b, 1 = 64b. MXETH only supports 32b DMA address bus width, so must set it 0.

11.1.8 ETH_TRANSMIT_STATUS

Description:	This register, when read, provides details of the status of a transmit. Once read, individual bits may be cleared by writing 1 to them. It is not possible to set a bit to 1 by writing to the register.
Address:	0x40481014
Offset:	0x1014
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LATE_COLLISION_OCCURRED [7:7]	TRANSMIT_UNDER_RUN123 [6:6]	TRANSMIT_COMPLETE123 [5:5]	AMBA_ERROR123 [4:4]	TRANSMIT_GO [3:3]	RETRY_LIMIT_EXCEEDED [2:2]	COLLISION_OCCURRED [1:1]	USED_BIT_READ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							RESP_NOT_OK123 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	USED_BIT_READ	RW1C	RW1C	0	Used bit read - set when a transmit buffer descriptor is read with its used bit set. Cleared by writing a one to this bit.
1	COLLISION_OCCURRED	RW1C	RW1C	0	Collision occurred - set by the assertion of collision. Cleared by writing a one to this bit. When operating in 10/100 mode, this status indicates either a collision or a late collision. In gigabit mode, this status is not set for a late collision.
2	RETRY_LIMIT_EXCEEDED	RW1C	RW1C	0	Retry limit exceeded - cleared by writing a one to this bit.
3	TRANSMIT_GO	R	R	0	Transmit go - if high transmit is active. When using the exposed FIFO interface, this bit represents bit 3 of the network control register. When using the DMA interface this bit represents the tx_go variable as specified in the transmit buffer description.
4	AMBA_ERROR123	RW1C	RW1C	0	Transmit frame corruption due to AMBA (AXI/AHB) errors. Set if an error occurs whilst midway through reading transmit frame from external memory including RRESP or BRESP errors and buffers exhausted mid frame (if the buffers run out during transmission of a frame then transmission stops, FCS shall be bad and tx_er asserted). Also set in DMA packet buffer mode if single frame is too large for configured packet buffer memory size. Cleared by writing a one to this bit.
5	TRANSMIT_COMPLETE123	RW1C	RW1C	0	Transmit complete - set when a frame has been transmitted. Cleared by writing a one to this bit.

Bits	Name	SW	HW	Default or Enum	Description
6	TRANSMIT_UNDER_RUN123	RW1C	RW1C	0	Transmit under run - this bit is set if the transmitter was forced to terminate a frame that it had already began transmitting due to further data being unavailable. This bit is set if a transmitter status write back has not completed when another status write back is attempted. When using the DMA interface configured for packet buffer mode, this bit will never be set. Cleared by writing a 1.
7	LATE_COLLISION_OCCURRED	RW1C	RW1C	0	Late collision occurred - only set if the condition occurs in gigabit mode, as retry is not attempted. Cleared by writing a one to this bit.
8	RESP_NOT_OK123	RW1C	RW1C	0	bresp/hresp not OK - set when the DMA block sees bresp/hresp not OK. Cleared by writing a one to this bit.

11.1.9 ETH_RECEIVE_Q_PTR

Description:	This register holds the start address of the receive buffer queue (receive buffers descriptor list). The receive buffer queue base address must be initialized before receive is enabled through bit 2 of the network control register. Once reception is enabled, any write to the receive buffer queue base address register is ignored. Reading this register returns the location of the descriptor currently being accessed. This value increments as buffers are used. Software should not use this register for determining where to remove received frames from the queue as it constantly changes as new frames are received. Software should instead work its way through the buffer descriptor queue checking the used bits. In terms of AMBA (AXI) operation, the receive descriptors are read from memory using a single 32bit AXI access. When the datapath is configured at 64bit, the receive descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is written to using a single 64bit AXI access.
Address:	0x40481018
Offset:	0x1018
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_RX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_RX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_RX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_RX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_RX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while receive is not enabled.
2:31	DMA_RX_Q_PTR	RW	RW	0	Receive buffer queue base address - written with the address of the start of the receive queue.

11.1.10 ETH_TRANSMIT_Q_PTR

Description: This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.

Address: 0x4048101C

Offset: 0x101C

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_TX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_TX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_TX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_TX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_TX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while transmit is not enabled.
2:31	DMA_TX_Q_PTR	RW	RW	0	Transmit buffer queue base address - written with the address of the start of the transmit queue.

11.1.11 ETH_RECEIVE_STATUS

Description: This register, when read provides details of the status of a receive. Once read, individual bits may be cleared by writing 1 to them. It is not possible to set a bit to 1 by writing to the register.

Address: 0x40481020

Offset: 0x1020

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				RESP_NOT_OK1234 [3:3]	RECEIVE_OVERRUN123 [2:2]	FRAME_RECEIVED [1:1]	BUFFER_NOT_AVAILABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BUFFER_NOT_AVAILABLE	RW1C	RW1C	0	Buffer not available - an attempt was made to get a new buffer and the pointer indicated that it was owned by the processor. The DMA will reread the pointer each time an end of frame is received until a valid pointer is found. This bit is set following each descriptor read attempt that fails, even if consecutive pointers are unsuccessful and software has in the mean time cleared the status flag. Cleared by writing a one to this bit.
1	FRAME_RECEIVED	RW1C	RW1C	0	Frame received - one or more frames have been received and placed in memory. Cleared by writing a one to this bit.
2	RECEIVE_OVERRUN123	RW1C	RW1C	0	Receive overrun - this bit is set if either the gem_dma RX FIFO or external RX FIFO were unable to store the receive frame due to a FIFO overflow, or if the receive status, reported by the gem_rx module to the gem_dma was not taken at end of frame. This bit is also set in DMA packet buffer mode if the packet buffer overflows. For DMA operation the buffer will be recovered if an overrun occurs. This bit is cleared by writing a one to it.
3	RESP_NOT_OK1234	RW1C	RW1C	0	brresp not OK - set when the DMA block sees brresp/hresp not OK. Cleared by writing a one to this bit.

11.1.12 ETH_INT_STATUS

Description: If not configured for priority queueing, the GEM generates a single interrupt. This register indicates the source of this interrupt. The corresponding bit in the mask register must be clear for a bit to be set. If any bit is set in this register the ethernet_int signal will be asserted. For test purposes each bit can be set or reset by writing to the interrupt mask register. The default configuration is shown below whereby all bits are reset to zero on read. Changing the validity of the `gem\_irq\_read\_clear` define will instead require a one to be written to the appropriate bit in order to clear it. In this mode reading has no affect on the status of the bit.

Address: 0x40481024
Offset: 0x1024
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT COMPLETE [7:7]	AMBA _ERROR [6:6]	RETRY LIMIT _EXCEEDE D_OR LATE COLLISION [5:5]	TRANSMIT UNDER _RUN [4:4]	TX_USED _BIT_READ [3:3]	RX_USED _BIT_READ [2:2]	RECEIVE _C OMplete [1:1]	MANAGEMENT _FRAME _SENT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	REMOVED _15 [15:15]	PAUSE _FRAME _TRANSMI TTED [14:14]	PAUSE _TIME _ELAPSED [13:13]	PAUSE _FRAME _WITH_NO N_ZERO _PAUSE _QUANTUM _RECEIVED [12:12]	RESP_NOT _OK [11:11]	RECEIVE _O VERRUN [10:10]	REMOVED _9 [9:9]	None [8:8]

Bits	23	22	21	20	19	18	17	16
Name	PTP _PDELAY _RESP _FRAME _RECEIVE D [23:23]	PTP _PDELAY _REQ _FRAME _RECEIVED [22:22]	PTP_SYNC _FRAME _TRAN SMITTED [21:21]	PTP _DELAY _REQ _FRAME _TRANSMIT TED [20:20]	PTP_SYNC _FRAME _RECE IVED [19:19]	PTP _DELAY _REQ _FRAME _RECEIVED [18:18]	REMOVED _17 [17:17]	REMOVED _16 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TSU _TIMER _COMPARISO N _INTERRUPT T [29:29]	REMOVED _28 [28:28]	RECEIVE _LPI _INDICAT ION _STATUS _BIT _CHANGE [27:27]	TSU _SECON DS _REGISTE R _INCREMENT T [26:26]	PTP _PDELAY _RESP _FRAME _TRANSMI TTED [25:25]	PTP _PDELAY _REQ _FRAME _TRANSMIT TED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MANAGEMENT_FRAME_SENT	RW1C	RW1C	0	Management frame sent - the PHY maintenance register has completed its operation. Cleared on read.
1	RECEIVE_COMPLETE	RW1C	RW1C	0	Receive complete - a frame has been stored in memory. Cleared on read.

Bits	Name	SW	HW	Default or Enum	Description
2	RX_USED_BIT_READ	RW1C	RW1C	0	RX used bit read - set when a receive buffer descriptor is read with its used bit set. Cleared on read.
3	TX_USED_BIT_READ	RW1C	RW1C	0	TX used bit read - set when a transmit buffer descriptor is read with its used bit set. Cleared on read.
4	TRANSMIT_UNDER_RUN	RW1C	RW1C	0	Transmit under run - this interrupt is set if the transmitter was forced to terminate a frame that it has already began transmitting due to further data being unavailable. If an under run occurs, the transmitter will force bad crc and tx_er high. This interrupt is set if a transmitter status write back has not completed when another status write back is attempted. When using the DMA interface configured for internal FIFO mode, this interrupt is also set when the transmit DMA has written the SOP data into the FIFO and either the AHB bus was not granted in time for further data, or because an AHB/AXI error response was returned by the connected slave, or because a used bit was read. When using the DMA interface configured for packet buffer mode, this bit will never be set. When using the external FIFO interface, this interrupt is also set when the tx_r_underflow input was asserted during a frame transfer. Cleared on read.
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION	RW1C	RW1C	0	Retry limit exceeded or late collision - transmit error. Late collision will only cause this status bit to be set in gigabit mode (as a retry is not attempted). Cleared on read.
6	AMBA_ERROR	RW1C	RW1C	0	Transmit frame corruption due to AMBA (AXI/AHB) error. Set if an error occurs whilst midway through reading transmit frame from external system memory, including HRESP (AHB), RRESP or BRESP(AXI) errors and buffers exhausted mid frame (if the buffers run out during transmission of a frame then transmission stops, FCS shall be bad and tx_er asserted). Also set in DMA packet buffer mode if single frame is too large for configured packet buffer memory size. Cleared on a read.
7	TRANSMIT_COMPLETE	W1C	W1C	0	Transmit complete - set when a frame has been transmitted. Cleared on read.
9	REMOVED_9	R	R	0	Write ignore, read 0
10	RECEIVE_OVERRUN	W1C	W1C	0	Receive overrun - set when the receive overrun status bit gets set. Cleared on read.
11	RESP_NOT_OK	W1C	W1C	0	bresp not OK - set when the DMA block sees bresp not OK. Cleared on read.
12	PAUSE_FRAME_WITH_NON_ZERO_PAUSE_QUANTUM_RECEIVED	W1C	W1C	0	Pause frame with non-zero pause quantum received - indicates a valid pause has been received that has a non-zero pause quantum field. Cleared on read.
13	PAUSE_TIME_ELAPSED	W1C	W1C	0	Pause Time elapsed. set when either the pause time register at address 0x38 decrements to zero, or when a valid pause frame is received with a zero pause quantum field. Cleared on read.
14	PAUSE_FRAME_TRANSMITTED	W1C	W1C	0	Pause frame transmitted - indicates a pause frame has been successfully transmitted after being initiated from the network control register or from the tx_pause control pin. Cleared on read.
15	REMOVED_15	R	R	0	Write ignore, read 0
16	REMOVED_16	R	R	0	Write ignore, read 0
17	REMOVED_17	R	R	0	Write ignore, read 0
18	PTP_DELAY_REQ_FRAME_RECEIVED	W1C	W1C	0	PTP delay_req frame received indicates a PTP delay_req frame has been received. Cleared on read.

Bits	Name	SW	HW	Default or Enum	Description
19	PTP_SYNC_FRAME_RECEIVED	W1C	W1C	0	PTP sync frame received indicates a PTP sync frame has been received. Cleared on read.
20	PTP_DELAY_REQ_FRAME_TRANSMITTED	W1C	W1C	0	PTP delay_req frame transmitted indicates a PTP delay_req frame has been transmitted. Cleared on read.
21	PTP_SYNC_FRAME_TRANSMITTED	W1C	W1C	0	PTP sync frame transmitted indicates a PTP sync frame has been transmitted. Cleared on read.
22	PTP_PDELAY_REQ_FRAME_RECEIVED	W1C	W1C	0	PTP pdelay_req frame received indicates a PTP pdelay_req frame has been received. Cleared on read.
23	PTP_PDELAY_RESP_FRAME_RECEIVED	W1C	W1C	0	PTP pdelay_resp frame received indicates a PTP pdelay_resp frame has been received. Cleared on read.
24	PTP_PDELAY_REQ_FRAME_TRANSMITTED	W1C	W1C	0	PTP pdelay_req frame transmitted indicates a PTP pdelay_req frame has been transmitted. Cleared on read.
25	PTP_PDELAY_RESP_FRAME_TRANSMITTED	W1C	W1C	0	PTP pdelay_resp frame transmitted indicates a PTP pdelay_resp frame has been transmitted. Cleared on read.
26	TSU_SECONDS_REGISTER_INCREMENT	W1C	W1C	0	TSU seconds register increment indicates the register has incremented. Cleared on read.
27	RECEIVE_LPI_INDICATION_STATUS_BIT_CHANGE	W1C	W1C	0	Receive LPI indication status bit change
28	REMOVED_28	R	R	0	Write ignore, read 0
29	TSU_TIMER_COMPARISON_INTERRUPT	W1C	W1C	0	TSU timer comparison interrupt. Indicates when TSU timer count value is equal to programmed value.

11.1.13 ETH_INT_ENABLE

Description:	At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.
Address:	0x40481028
Offset:	0x1028
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ENABLE_TR ANSMIT _COM _PLETE _INTE RRUPT [7:7]	ENABLE_TR ANSMIT _FRAME _CORRUPT _ION_DUE _TO_AMBA _ERROR _INTERRUPT [6:6]	ENABLE_RETRY _LIMIT EXCEEDED _OR_LATE _COL LISION_INT ERRUPT [5:5]	ENABLE_TR ANSMIT _BUFFER _UNDER _RUN _INTERR UPT [4:4]	ENABLE_TR ANSMIT _USED_BIT _READ _INTERRUPT [3:3]	ENABLE_RECEIVE _USED_BIT _READ _INTERRUPT [2:2]	ENABLE_RECEIVE _COMP _LETE _INTER RUPT [1:1]	ENABLE_MA NAGEMENT _DONE _INTERR UPT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	UNUSED_15 [15:15]	ENABLE_PAUSE _FRAME TRANSMITTE D _INTERRUPT [14:14]	ENABLE_PAUSE _TIME_Z ERO _INTERR UPT [13:13]	ENABLE_PAUSE _FRAME WITH_NON ZERO _PAUSE QUANTUM _IN TERRUPT [12:12]	ENABLE_RESP _NOT_OK _INTERRUPT [11:11]	ENABLE_RECEIVE _OVER _RUN _INTERR UPT [10:10]	UNUSED_9 [9:9]	UNUSED_8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	ENABLE_PTP _PDELAY _RESP _FRAME _RECEIVED [23:23]	ENABLE_PTP _PDELAY _REQ _FRAME_R _ECEIVED [22:22]	ENABLE_PTP _SYNC _FRAME _TRANSMI TTED [21:21]	ENABLE_PTP _DELAY _REQ _FRAME _TR ANSMITTED [20:20]	ENABLE_PTP _SYNC _FRAME _RECEIVE D [19:19]	ENABLE_PTP _DELAY _REQ _FRAME _RE CEIVED [18:18]	UNUSED_17 [17:17]	UNUSED_16 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		ENABLE_TSU _TIMER _CO MPARISON _I NTERRUPT [29:29]	UNUSED_28 [28:28]	ENABLE_RX_LPI _INDIC ATION _INTE RRUPT [27:27]	ENABLE_TSU _SECONDS _REGISTER _I NCREMENT [26:26]	ENABLE_PTP _PDELAY _RESP _FRAME TRANSMITTER D [25:25]	ENABLE_PTP _PDELAY _REQ _FRAME_T RANSMITTED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE_MANAGEMENT_DONE_INTERRUPT	W	W	0	Enable management done interrupt

Bits	Name	SW	HW	Default or Enum	Description
1	ENABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	Enable receive complete interrupt
2	ENABLE_RECEIVE_USED_BIT_READ_INTERRUPT	W	W	0	Enable receive used bit read interrupt
3	ENABLE_TRANSMIT_USED_BIT_READ_INTERRUPT	W	W	0	Enable transmit used bit read interrupt
4	ENABLE_TRANSMIT_BUFFER_UNDER_RUN_INTERRUPT	W	W	0	Enable transmit buffer under run interrupt
5	ENABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	Enable retry limit exceeded or late collision interrupt
6	ENABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	Enable transmit frame corruption due to AMBA (AXI/AHB) error interrupt
7	ENABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	Enable transmit complete interrupt
8	UNUSED_8	W	W	0	Not used
9	UNUSED_9	W	W	0	Not used
10	ENABLE_RECEIVE_OVERRUN_INTERRUPT	W	W	0	Enable receive overrun interrupt
11	ENABLE_RESP_NOT_OK_INTERRUPT	W	W	0	Enable bresp not OK interrupt
12	ENABLE_PAUSE_FRAME_WITH_NON_ZERO_PAUSE_QUANTUM_INTERRUPT	W	W	0	Enable pause frame with non-zero pause quantum interrupt
13	ENABLE_PAUSE_TIME_ZERO_INTERRUPT	W	W	0	Enable pause time zero interrupt
14	ENABLE_PAUSE_FRAME_TRANSMITTED_INTERRUPT	W	W	0	Enable pause frame transmitted interrupt
15	UNUSED_15	W	W	0	Not used
16	UNUSED_16	W	W	0	Not used
17	UNUSED_17	W	W	0	Not used
18	ENABLE_PTP_DELAY_REQ_FRAME_RECEIVED	W	W	0	Enable PTP delay_req frame received
19	ENABLE_PTP_SYNC_FRAME_RECEIVED	W	W	0	Enable PTP sync frame received
20	ENABLE_PTP_DELAY_REQ_FRAME_TRANSMITTED	W	W	0	Enable PTP delay_req frame transmitted
21	ENABLE_PTP_SYNC_FRAME_TRANSMITTED	W	W	0	Enable PTP sync frame transmitted
22	ENABLE_PTP_PDELAY_REQ_FRAME_RECEIVED	W	W	0	Enable PTP pdelay_req frame received
23	ENABLE_PTP_PDELAY_RESP_FRAME_RECEIVED	W	W	0	Enable PTP pdelay_resp frame received

Bits	Name	SW	HW	Default or Enum	Description
24	ENABLE_PTP_PDELAY_REQ_FRAME_TRANSMITTED	W	W	0	Enable PTP pdelay_req frame transmitted
25	ENABLE_PTP_PDELAY_RESP_FRAME_TRANSMITTED	W	W	0	Enable PTP pdelay_resp frame transmitted
26	ENABLE_TSU_SECONDS_REGISTER_INCREMENT	W	W	0	Enable TSU seconds register increment
27	ENABLE_RX_LPI_INDICATION_INTERRUPT	W	W	0	Enable RX LPI indication interrupt
28	UNUSED_28	W	W	0	Not used
29	ENABLE_TSU_TIMER_COMPARISON_INTERRUPT	W	W	0	Enable TSU timer comparison interrupt.

11.1.14 ETH_INT_DISABLE

Description: Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.

Address: 0x4048102C

Offset: 0x102C

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DISABLE_TRANSMIT_COMPLETE_INTERRUPT [7:7]	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT [6:6]	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT [5:5]	DISABLE_TRANSMIT_BUFFER_UNDER_RUN_INTERRUPT [4:4]	DISABLE_TRANSMIT_USED_BIT_READ_INTERRUPT [3:3]	DISABLE_RECEIVE_USED_BIT_READ_INTERRUPT [2:2]	DISABLE_RECEIVE_COMPLETE_INTERRUPT [1:1]	DISABLE_MANAGEMENT_DONE_INTERRUPT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	UNUSED_15 [15:15]	DISABLE_PAUSE_FRAME_TRANSMITTED_INTERRUPT [14:14]	DISABLE_PAUSE_TIME_ZERO_INTERRUPT [13:13]	DISABLE_PAUSE_FRAME_WITH_NON_ZERO_PAUSE_QUANTUM_INTERRUPT [12:12]	DISABLE_RESP_NOT_OK_INTERRUPT [11:11]	DISABLE_RECEIVE_OVERFLOW_RRUN_INTERRUPT [10:10]	UNUSED_9 [9:9]	UNUSED_8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	DISABLE_PAUSE_DELAY_RESP_FRAME_RECEIVED [23:23]	DISABLE_PAUSE_DELAY_REQ_FRAME_RECEIVED [22:22]	DISABLE_PAUSE_SYNC_FRAME_TRANSMITTED [21:21]	DISABLE_PAUSE_DELAY_REQ_FRAME_TRANSMITTED [20:20]	DISABLE_PAUSE_SYNC_FRAME_RECEIVED [19:19]	DISABLE_PAUSE_DELAY_REQ_FRAME_RECEIVED [18:18]	UNUSED_17 [17:17]	UNUSED_16 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_31 [31:31]	RESERVED_30_30 [30:30]	DISABLE_SUS_TIMER_COMPARISON_INTERRUPT [29:29]	UNUSED_28 [28:28]	DISABLE_RX_LPI_INDICATION_INTERRUPT [27:27]	DISABLE_SUS_SECONDS_REGISTER_INCREMENT [26:26]	DISABLE_PAUSE_DELAY_RESP_FRAME_TRANSMITTED [25:25]	DISABLE_PAUSE_DELAY_REQ_FRAME_TRANSMITTED [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DISABLE_MANAGEMENT_DONE_INTERRUPT	W	W	0	'Disable management done interrupt'
1	DISABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	'Disable receive complete interrupt'

Bits	Name	SW	HW	Default or Enum	Description
2	DISABLE_RECEIVE_USED_BIT_READ_INTERRUPT	W	W	0	'Disable receive used bit read interrupt'
3	DISABLE_TRANSMIT_USED_BIT_READ_INTERRUPT	W	W	0	'Disable transmit used bit read interrupt'
4	DISABLE_TRANSMIT_BUFFER_UNDER_RUN_INTERRUPT	W	W	0	'Disable transmit buffer under run interrupt'
5	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	'Disable retry limit exceeded or late collision interrupt'
6	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	'Disable transmit frame corruption due to AMBA (AHB/AXI) error interrupt'
7	DISABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	'Disable transmit complete interrupt'
8	UNUSED_8	W	W	0	Not used
9	UNUSED_9	W	W	0	Not used
10	DISABLE_RECEIVE_OVERRUN_INTERRUPT	W	W	0	'Disable receive overrun interrupt'
11	DISABLE_RESP_NOT_OK_INTERRUPT	W	W	0	'Disable bresp/hresp not OK interrupt'
12	DISABLE_PAUSE_FRAME_WITH_NON_ZERO_PAUSE_QUANTUM_INTERRUPT	W	W	0	'Disable pause frame with non-zero pause quantum interrupt'
13	DISABLE_PAUSE_TIME_ZERO_INTERRUPT	W	W	0	'Disable pause time zero interrupt'
14	DISABLE_PAUSE_FRAME_TRANSMITTED_INTERRUPT	W	W	0	'Disable pause frame transmitted interrupt'
15	UNUSED_15	W	W	0	Not used
16	UNUSED_16	W	W	0	Not used
17	UNUSED_17	W	W	0	Not used
18	DISABLE_PTP_DELAY_REQ_FRAME_RECEIVED	W	W	0	'Disable PTP delay_req frame received'
19	DISABLE_PTP_SYNC_FRAME_RECEIVED	W	W	0	'Disable PTP sync frame received'
20	DISABLE_PTP_DELAY_REQ_FRAME_TRANSMITTED	W	W	0	'Disable PTP delay_req frame transmitted '
21	DISABLE_PTP_SYNC_FRAME_TRANSMITTED	W	W	0	'Disable PTP sync frame transmitted '
22	DISABLE_PTP_PDELAY_REQ_FRAME_RECEIVED	W	W	0	'Disable PTP pdelay_req frame received'
23	DISABLE_PTP_PDELAY_RESP_FRAME_RECEIVED	W	W	0	'Disable PTP pdelay_resp frame received'
24	DISABLE_PTP_PDELAY_REQ_FRAME_TRANSMITTED	W	W	0	'Disable PTP pdelay_req frame transmitted'

Bits	Name	SW	HW	Default or Enum	Description
25	DISABLE_PTP_PDELAY_RESP_FRAME_TRANSMITTED	W	W	0	'Disable PTP pdelay_resp frame transmitted'
26	DISABLE_TSU_SECONDS_REGISTER_INCREMENT	W	W	0	'Disable TSU seconds register increment'
27	DISABLE_RX_LPI_INDICATION_INTERRUPT	W	W	0	'Disable RX LPI indication interrupt'
28	UNUSED_28	W	W	0	Not used
29	DISABLE_TSU_TIMER_COMPARISON_INTERRUPT	W	W	0	'Disable TSU timer comparison interrupt.'
30	RESERVED_30_30	R	R	0	'Reserved, read as 0, ignored on write.'
31	RESERVED_31_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.15 ETH_INT_MASK

Description: The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.

Address: 0x40481030
Offset: 0x1030
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x3FFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT COMPLETE _INTERRUPT _MASK [7:7]	AMBA ERROR _INTERRUPT _MASK [6:6]	RETRY LIMIT _EXCEEDED_OR LATE COLLISION _MASK [5:5]	TRANSMIT BUFFER _UNDER RUN_INTERRUPT _MASK [4:4]	TRANSMIT USED_BIT _READ_INTERRUPT _MASK [3:3]	RECEIVE USED_BIT _READ_INTERRUPT _MASK [2:2]	RECEIVE _COMPLETE_INTERRUPT _MASK [1:1]	MANAGEMENT_DONE_INTERRUPT_MASK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	UNUSED_15 [15:15]	PAUSE_FRAME_TRANSMITTED_INTERRUPT_MASK [14:14]	PAUSE_TIME_ZERO_INTERRUPT_MASK [13:13]	PAUSE_FRAME_WITH_NO_ZERO_PAUSE_QUANTUM_INTERRUPT_MASK [12:12]	RESP_NOT_OK_INTERRUPT_MASK [11:11]	RECEIVE_OVERFLOW_INTERRUPT_MASK [10:10]	UNUSED_9 [9:9]	UNUSED_8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	PTP_DELAY_RESP_FRAME_RECEIVED_MASK [23:23]	PTP_DELAY_REQ_FRAME_RECEIVED_MASK [22:22]	PTP_SYNC_FRAME_TRANSMITTED_MASK [21:21]	PTP_DELAY_REQ_FRAME_TRANSMITTED_MASK [20:20]	PTP_SYNC_FRAME_RECEIVED_MASK [19:19]	PTP_DELAY_REQ_FRAME_RECEIVED_MASK [18:18]	UNUSED_17 [17:17]	UNUSED_16 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TSU_TIMER_COMPARISON_MASK [29:29]	UNUSED_28 [28:28]	RX_LPI_INDICATION_MASK [27:27]	TSU_SECONDS_REGISTER_INCREMENT_MASK [26:26]	PTP_DELAY_RESP_FRAME_TRANSMITTED_MASK [25:25]	PTP_DELAY_REQ_FRAME_TRANSMITTED_MASK [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MANAGEMENT_DONE_INTERRUPT_MASK	R	R	1	management done interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
1	RECEIVE_COMPLETE_INTERRUPT_MASK	R	R	1	receive complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
2	RECEIVE_USED_BIT_READ_INTERRUPT_MASK	R	R	1	receive used bit read interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
3	TRANSMIT_USED_BIT_READ_INTERRUPT_MASK	R	R	1	transmit used bit read interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
4	TRANSMIT_BUFFER_UNDER_RUN_INTERRUPT_MASK	R	R	1	transmit buffer under run interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_MASK	R	R	1	A read of this register returns the value of the retry limit exceeded or late collision (gigabit mode only) interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
6	AMBA_ERROR_INTERRUPT_MASK	R	R	1	transmit frame corruption due to AMBA (AXI) error interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
7	TRANSMIT_COMPLETE_INTERRUPT_MASK	R	R	1	transmit complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
8	UNUSED_8	R	R	1	Not used
9	UNUSED_9	R	R	1	Not used
10	RECEIVE_OVERRUN_INTERRUPT_MASK	R	R	1	receive overrun interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

Bits	Name	SW	HW	Default or Enum	Description
11	RESP_NOT_OK_INTERRUPT_MASK	R	R	1	bresp not OK interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
12	PAUSE_FRAME_WITH_NON_ZERO_PAUSE_QUANTUM_INTERRUPT_MASK	R	R	1	pause frame with non-zero pause quantum interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
13	PAUSE_TIME_ZERO_INTERRUPT_MASK	R	R	1	pause time zero interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
14	PAUSE_FRAME_TRANSMITTED_INTERRUPT_MASK	R	R	1	pause frame transmitted interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
15	UNUSED_15	R	R	1	Not used
16	UNUSED_16	R	R	1	Not used
17	UNUSED_17	R	R	1	Not used
18	PTP_DELAY_REQ_FRAME_RECEIVED_MASK	R	R	1	A read of this register returns the value of the PTP delay_req frame received mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
19	PTP_SYNC_FRAME_RECEIVED_MASK	R	R	1	A read of this register returns the value of the PTP sync frame received mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
20	PTP_DELAY_REQ_FRAME_TRANSMITTED_MASK	R	R	1	A read of this register returns the value of the PTP delay_req frame transmitted mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
21	PTP_SYNC_FRAME_TRANSMITTED_MASK	R	R	1	A read of this register returns the value of the PTP sync frame transmitted mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

Bits	Name	SW	HW	Default or Enum	Description
22	PTP_PDELAY_REQ_FRAME_RECEIVED_MASK	R	R	1	A read of this register returns the value of the PTP pdelay_req frame received mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
23	PTP_PDELAY_RESP_FRAME_RECEIVED_MASK	R	R	1	A read of this register returns the value of the PTP pdelay_resp frame received mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
24	PTP_PDELAY_REQ_FRAME_TRANSMITTED_MASK	R	R	1	A read of this register returns the value of the PTP pdelay_req frame transmitted mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
25	PTP_PDELAY_RESP_FRAME_TRANSMITTED_MASK	R	R	1	A read of this register returns the value of the PTP pdelay_resp frame transmitted mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
26	TSU_SECONDS_REGISTER_INCREMENT_MASK	R	R	1	A read of this register returns the value of the TSU seconds register increment mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
27	RX_LPI_INDICATION_MASK	R	R	1	A read of this register returns the value of the RX LPI indication mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
28	UNUSED_28	R	R	1	unused
29	TSU_TIMER_COMPARISON_MASK	R	R	1	Enable TSU timer comparison interrupt mask.

11.1.16 ETH_PHY_MANAGEMENT

Description: The PHY maintenance register is implemented as a shift register. Writing to the register starts a shift operation which is signalled as complete when bit-2 is set in the network status register. It takes about 2000 pclk cycles to complete, when MDC is set for pclk divide by 32 in the network configuration register. An interrupt is generated upon completion. During this time, the MSB of the register is output on the MDIO pin and the LSB updated from the MDIO pin with each MDC cycle. This causes transmission of a PHY management frame on MDIO. See Section 22.2.4.5 of the IEEE 802.3 standard. Reading during the shift operation will return the current contents of the shift register. At the end of management operation, the bits will have shifted back to their original locations. For a read operation, the data bits will be updated with data read from the PHY. It is important to write the correct values to the register to ensure a valid PHY management frame is produced. The MDIO interface can read IEEE 802.3 clause 45 PHYs as well as clause 22 PHYs. To read clause 45 PHYs, bit 30 should be written with a 0 rather than a 1. For a description of MDC generation, see Network Configuration Register.

Address: 0x40481034
Offset: 0x1034
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PHY_WRITE_READ_DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	PHY_WRITE_READ_DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	REGISTER_ADDRESS [22:18]						WRITE10 [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	WRITE0 [31:31]	WRITE1 [30:30]	OPERATION [29:28]		PHY_ADDRESS [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	PHY_WRITE_READ_DATA	RW	RW	0	For a write operation this is written with the data to be written to the PHY. After a read operation this contains the data read from the PHY.
16:17	WRITE10	RW	RW	0	Must be written with 10.
18:22	REGISTER_ADDRESS	RW	RW	0	Register address - specifies the register in the PHY to access.
23:27	PHY_ADDRESS	RW	RW	0	PHY address.
28:29	OPERATION	RW	RW	0	Operation. For a Clause 45 frame: 00 is an addr, 01 is a write, 10 is a post read increment, 11 is a read frame. For a Clause 22 frame: 10 is a read, 01 is a write.
30	WRITE1	RW	RW	0	Must be written to 1 for a valid Clause 22 frame and to 0 for a valid Clause 45 frame.
31	WRITE0	RW	RW	0	Must be written with 0.

11.1.17 ETH_PAUSE_TIME

Description: Received Pause Quantum Register
Address: 0x40481038
Offset: 0x1038
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QUANTUM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	QUANTUM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	QUANTUM	R	R	0	Received pause quantum - stores the current value of the received pause quantum register which is decremented every 512 bit times.

11.1.18 ETH_TX_PAUSE_QUANTUM

Description: Transmit Pause Quantum Register
Address: 0x4048103C
Offset: 0x103C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QUANTUM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	QUANTUM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	QUANTUM_P1 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	QUANTUM_P1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	QUANTUM	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission.
16:31	QUANTUM_P1	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 1.

11.1.19 ETH_PBUF_TXCUTTHRU

Description: Partial store and forward is only applicable when using the DMA configured in SRAM based packet buffer mode. It is also not available when using multi buffer frames. TX Partial Store and Forward

Address: 0x40481040

Offset: 0x1040

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x1FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_TX_CUTTHRU_THRESHOLD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							DMA_TX_CUTTHRU_THRESHOLD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_TX_CUTTHRU [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	DMA_TX_CUTTHRU_THRESHOLD	RW	RW	511	Watermark value. This value must be $\geq 0x9$. The reset value depends on the value of the configuration option `gem_tx_pbuf_addr`, which is defined in the verilog defs configuration file. The value chosen for the generation of the userguide was `gem_tx_pbuf_addr = 9`
31	DMA_TX_CUTTHRU	RW	RW	0	Enable TX partial store and forward operation

11.1.20 ETH_PBUF_RXCUTTHRU

Description: RX Partial Store and Forward
Address: 0x40481044
Offset: 0x1044
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_RX_CUTTHRU_THRESHOLD [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DMA_RX_CUTTHRU [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DMA_RX_CUTTHRU_THRESHOLD	RW	RW	255	Watermark value. The reset value depends on the value of the configuration option `gem_rx_pbuf_addr`, which is defined in the verilog defs configuration file. The value chosen for the generation of the userguide was `gem_rx_pbuf_addr = 8`.
31	DMA_RX_CUTTHRU	RW	RW	0	Enable RX partial store and forward operation

11.1.21 ETH_JUMBO_MAX_LENGTH

Description: Maximum Jumbo Frame Size.
Address: 0x40481048
Offset: 0x1048
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x600

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	JUMBO_MAX_LENGTH [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		JUMBO_MAX_LENGTH [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:13	JUMBO_MAX_LENGTH	RW	RW	1536	Maximum Jumbo Frame Size - resets to the gem_jumbo_max_length define value.

11.1.22 ETH_EXTERNAL_FIFO_INTERFACE

Description: Not presents.
Address: 0x4048104C
Offset: 0x104C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.23 ETH_RSC_CONTROL

Description: Not presents. Access to the register will return AHB error.
Address: 0x40481058
Offset: 0x1058
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.24 ETH_INT_MODERATION

Description:	Used to moderate the number of transmit and receive complete interrupts issued. With interrupt moderation enabled receive and transmit interrupts are not generated immediately a frame is transmitted or received. Instead when a receive or transmit event occurs a timer is started and the interrupt is asserted after it times out. This limits the frequency with which the CPU receives interrupts. When interrupt moderation is enabled interrupt status bit one is always used for receive and bit 7 is always used for transmit even when priority queuing is enabled. With interrupt moderation 800ns periods are counted. GEM determines what constitutes an 800ns period by looking at the tbi (bit 11), gigabit bit (10) and speed (bit 0) bits in the network configuration register and counting tx_clk cycles. Bit 0 needs to be set to 1 for 100M operation.
Address:	0x4048105C
Offset:	0x105C
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RX_INT_MODERATION [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TX_INT_MODERATION [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	RX_INT_MODERATION	RW	RW	0	Count of 800ns periods before bit 1 is set in the interrupt status register after a frame is received. A non-zero value indicates receive interrupt moderation will be performed.
16:23	TX_INT_MODERATION	RW	RW	0	Count of 800ns periods before bit 7 is set in the interrupt status register after a frame is transmitted. A non-zero value indicates transmit interrupt moderation will be performed.

11.1.25 ETH_SYS_WAKE_TIME

Description: Used to pause transmission after deassertion of tx_lpi_en. Each unit in this register corresponds to 64ns in gigabit mode, 320ns in 100M mode and 3200ns at 10M. After tx_lpi_en is deasserted transmission will pause for the set time.

Address: 0x40481060

Offset: 0x1060

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SYS_WAKE_TIME [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	SYS_WAKE_TIME [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	SYS_WAKE_TIME	RW	RW	0	Count of 64ns, 320ns or 3200ns intervals before transmission starts after deassertion of tx_lpi_en (each interval is equivalent to eight tx_clk periods and so varies with data rate).

11.1.26 ETH_HASH_BOTTOM

Description: The unicast hash enable and the multicast hash enable bits in the network configuration register enable the reception of hash matched frames. Hash Register Bottom (31 to 0 bits)

Address: 0x40481080

Offset: 0x1080

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_HASH_B [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_HASH_B [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_HASH_B [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_HASH_B [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_HASH_B	RW	RW	0	The first 32 bits of the hash address register.

11.1.27 ETH_HASH_TOP

Description: Hash Register Top (63 to 32 bits)
Address: 0x40481084
Offset: 0x1084
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_HASH_T [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_HASH_T [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_HASH_T [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_HASH_T [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_HASH_T	RW	RW	0	The remaining 32 bits of the hash address register.

11.1.28 ETH_SPEC_ADD1_BOTTOM

Description:	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
Address:	0x40481088
Offset:	0x1088
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_ADD1_B [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_ADD1_B [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_ADD1_B [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_ADD1_B [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_ADD1_B	RW	RW	0	'Least significant 32 bits of the destination address, that is bits 31:0. Bit zero indicates whether the address is multicast or unicast and corresponds to the least significant bit of the first byte received.'

11.1.29 ETH_SPEC_ADD1_TOP

Description: Specific Address Top
Address: 0x4048108C
Offset: 0x108C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_TOP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_TOP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							FILTER_TY PE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDRESS_TOP	RW	RW	0	Specific address 1. The most significant bits of the destination/source address that is to be compared, that is bits 47:32.
16	FILTER_TYPE	RW	RW	0	This control bit selects whether this filter should be comparing the MAC source address or the MAC destination address of the received Ethernet frame. When set to zero, the filter is a destination address filter. When set to one, the filter is a source address filter. Specific address 1. The most significant bits of the destination address, that is bits 47:32.

11.1.30 ETH_SPEC_ADD2_BOTTOM

Description:	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
Address:	0x40481090
Offset:	0x1090
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_BOTTOM [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_BOTTOM [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_BOTTOM [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_BOTTOM	RW	RW	0	Least significant 32 bits of the destination address, that is bits 31:0. Bit zero indicates whether the address is multicast or unicast and corresponds to the least significant bit of the first byte received.

11.1.31 ETH_SPEC_ADD2_TOP

Description: Specific Address Top
Address: 0x40481094
Offset: 0x1094
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_TOP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_TOP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							FILTER_TYPE [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		FILTER_BYTE_MASK [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDRESS_TOP	RW	RW	0	Specific address 1. The most significant bits of the destination/source address that is to be compared, that is bits 47:32.
16	FILTER_TYPE	RW	RW	0	This control bit selects whether this filter should be comparing the MAC source address or the MAC destination address of the received Ethernet frame. When set to zero, the filter is a destination address filter. When set to one, the filter is a source address filter. Specific address 1. The most significant bits of the destination address, that is bits 47:32.
24:29	FILTER_BYTE_MASK	RW	RW	0	When high, the associated byte of the specific address will not be compared. Bit 24 controls whether the first byte received should be compared. Bit 29 controls whether the last byte received should be compared.

11.1.32 ETH_SPEC_ADD3_BOTTOM

Description:	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
Address:	0x40481098
Offset:	0x1098
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_BOTTOM [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_BOTTOM [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_BOTTOM [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_BOTTOM	RW	RW	0	Least significant 32 bits of the destination address, that is bits 31:0. Bit zero indicates whether the address is multicast or unicast and corresponds to the least significant bit of the first byte received.

11.1.33 ETH_SPEC_ADD3_TOP

Description: Specific Address Top
Address: 0x4048109C
Offset: 0x109C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_TOP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_TOP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							FILTER_TYPE [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		FILTER_BYTE_MASK [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDRESS_TOP	RW	RW	0	Specific address 1. The most significant bits of the destination/source address that is to be compared, that is bits 47:32.
16	FILTER_TYPE	RW	RW	0	This control bit selects whether this filter should be comparing the MAC source address or the MAC destination address of the received Ethernet frame. When set to zero, the filter is a destination address filter. When set to one, the filter is a source address filter. Specific address 1. The most significant bits of the destination address, that is bits 47:32.
24:29	FILTER_BYTE_MASK	RW	RW	0	When high, the associated byte of the specific address will not be compared. Bit 24 controls whether the first byte received should be compared. Bit 29 controls whether the last byte received should be compared.

11.1.34 ETH_SPEC_ADD4_BOTTOM

Description:	The addresses stored in the specific address registers are deactivated at reset or when their corresponding specific address register bottom is written. They are activated when specific address register top is written.
Address:	0x404810A0
Offset:	0x10A0
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_BOTTOM [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_BOTTOM [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_BOTTOM [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_BOTTOM	RW	RW	0	Least significant 32 bits of the destination address, that is bits 31:0. Bit zero indicates whether the address is multicast or unicast and corresponds to the least significant bit of the first byte received.

11.1.35 ETH_SPEC_ADD4_TOP

Description: Specific Address Top
Address: 0x404810A4
Offset: 0x10A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_TOP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_TOP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							FILTER_TYPE [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		FILTER_BYTE_MASK [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDRESS_TOP	RW	RW	0	Specific address 1. The most significant bits of the destination/source address that is to be compared, that is bits 47:32.
16	FILTER_TYPE	RW	RW	0	This control bit selects whether this filter should be comparing the MAC source address or the MAC destination address of the received Ethernet frame. When set to zero, the filter is a destination address filter. When set to one, the filter is a source address filter. Specific address 1. The most significant bits of the destination address, that is bits 47:32.
24:29	FILTER_BYTE_MASK	RW	RW	0	When high, the associated byte of the specific address will not be compared. Bit 24 controls whether the first byte received should be compared. Bit 29 controls whether the last byte received should be compared.

11.1.36 ETH_SPEC_TYPE1

Description: Type ID Match 1
Address: 0x404810A8
Offset: 0x10A8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MATCH [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MATCH [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE_COPY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MATCH	RW	RW	0	Type ID match 1. For use in comparisons with received frames type ID/length field.
31	ENABLE_COPY	RW	RW	0	Enable copying of type ID match 1 matched frames.

11.1.37 ETH_SPEC_TYPE2

Description: Type ID Match 2
Address: 0x404810AC
Offset: 0x10AC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MATCH [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MATCH [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE_COPY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MATCH	RW	RW	0	Type ID match 2. For use in comparisons with received frames type ID/length field.
31	ENABLE_COPY	RW	RW	0	Enable copying of type ID match 2 matched frames.

11.1.38 ETH_SPEC_TYPE3

Description: Type ID Match 3
Address: 0x404810B0
Offset: 0x10B0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MATCH [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MATCH [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE_COPY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MATCH	RW	RW	0	Type ID match 3. For use in comparisons with received frames type ID/length field.
31	ENABLE_COPY	RW	RW	0	Enable copying of type ID match 3 matched frames.

11.1.39 ETH_SPEC_TYPE4

Description: Type ID Match 4
Address: 0x404810B4
Offset: 0x10B4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MATCH [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MATCH [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE_COPY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MATCH	RW	RW	0	Type ID match 4. For use in comparisons with received frames type ID/length field.
31	ENABLE_COPY	RW	RW	0	Enable copying of type ID match 4 matched frames.

11.1.40 ETH_WOL_REGISTER

Description: Wake on LAN Register. Presents in design, but feature is not supported.
Address: 0x404810B8
Offset: 0x10B8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				WOL_MASK_3 [19:19]	WOL_MASK_2 [18:18]	WOL_MASK_1 [17:17]	WOL_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDR	RW	RW	0	Wake on LAN ARP request IP address. Written to define the least significant 16 bits of the target IP address that is matched to generate a Wake on LAN event. A value of zero will not generate an event, even if this is matched by the received frame.
16	WOL_MASK_0	RW	RW	0	Wake on LAN magic packet event enable. When set magic packet events will cause the wol output to be asserted.
17	WOL_MASK_1	RW	RW	0	Wake on LAN ARP request event enable. When set ARP request events will cause the wol output to be asserted.
18	WOL_MASK_2	RW	RW	0	Wake on LAN specific address register 1 event enable. When set specific address 1 events will cause the wol output to be asserted.
19	WOL_MASK_3	RW	RW	0	Wake on LAN multicast hash event enable. When set multicast hash events will cause the wol output to be asserted.

11.1.41 ETH_STRETCH_RATIO

Description: IPG stretch register
Address: 0x404810BC
Offset: 0x10BC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IPG_STRETCH [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	IPG_STRETCH [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	IPG_STRETCH	RW	RW	0	IPG Stretch. Bits 7:0 are multiplied with the previously transmitted frame length (including preamble) bits 15:8 +1 divide the frame length. If the resulting number is greater than 96 and bit 28 is set in the network configuration register then the resulting number is used for the transmit inter-packet-gap. 1 is added to bits 15:8 to prevent a divide by zero.

11.1.42 ETH_STACKED_VLAN

Description: Stacked VLAN Register
Address: 0x404810C0
Offset: 0x10C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MATCH [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MATCH [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE_PROCESSING [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MATCH	RW	RW	0	User defined VLAN_TYPE field. When Stacked VLAN is enabled, the first VLAN tag in a received frame will only be accepted if the VLAN type field is equal to this user defined VLAN_TYPE OR equal to the standard VLAN type (0x8100). Note that the second VLAN tag of a Stacked VLAN packet will only be matched correctly if its VLAN_TYPE field equals 0x8100.
31	ENABLE_PROCESSING	RW	RW	0	Enable stacked VLAN processing mode

11.1.43 ETH_TX_PFC_PAUSE

Description: Transmit PFC Pause Register
Address: 0x404810C4
Offset: 0x10C4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VECTOR_ENABLE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VECTOR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	VECTOR_ENABLE	RW	RW	0	Priority Vector Enable. If bit 17 of the network control register is written with a one then the priority enable vector of the PFC priority based pause frame will be set equal to the value stored in this register [7:0].
8:15	VECTOR	RW	RW	0	Priority Vector Pause Size. If bit 17 of the network control register is written with a one then for each entry equal to zero in the Transmit PFC Pause Register[15:8], the PFC pause frame's pause quantum field associated with that entry will be taken from the transmit pause quantum register. For each entry equal to one in the Transmit PFC Pause Register [15:8], the pause quantum associated with that entry will be zero.

11.1.44 ETH_MASK_ADD1_BOTTOM

Description: Specific Address Mask 1 Bottom (31 to 0 bits)
Address: 0x404810C8
Offset: 0x10C8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_MASK_BOTTOM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_MASK_BOTTOM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_MASK_BOTTOM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_MASK_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_MASK_BOTTOM	RW	RW	0	Specific Address Mask. Setting a bit to one masks the corresponding bit in the specific address 1 register (31 to 0 bits)

11.1.45 ETH_MASK_ADD1_TOP

Description: Specific Address Mask 1 Top (47 to 32 bits)
Address: 0x404810CC
Offset: 0x10CC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_MASK_TOP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_MASK_TOP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ADDRESS_MASK_TOP	RW	RW	0	Specific Address Mask. Setting a bit to one masks the corresponding bit in the specific address 1 register (47 to 32 bits).

11.1.46 ETH_DMA_ADDR_OR_MASK

Description: Receive DMA Data Buffer Address Mask
Address: 0x404810D0
Offset: 0x10D0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				MASK_ENABLE [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MASK_VALUE_DA [31:28]				None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	MASK_ENABLE	RW	RW	0	Data Buffer Address Mask Enable. These bits are associated directly with bits[31:28].When bit 0 is set, the AXI/AHB address bit 28 used for accessing the receive data buffers will be forced to the value stored in bit 28 of this register. When bit 1 is set, the AXI/AHB address bit 29 used for accessing the receive data buffers will be forced to the value stored in bit 29 of this register. When bit 2 is set, the AXI/AHB address bit 30 used for accessing the receive data buffers will be forced to the value stored in bit 30 of this register. When bit 3 is set, the AXI/AHB address bit 31 used for accessing the receive data buffers will be forced to the value stored in bit 31 of this register. When these bits are clear, the associated value stored in bits 31:28 have no effect on the AXI/AHB address used for receive data buffer accesses. Any changes to this register will be ignored while the DMA is currently processing a receive packet. It will only affect the next full packet to be written to external memory.
28:31	MASK_VALUE_DA	RW	RW	0	Data Buffer Address Mask Value. Values used to force bits 31:28 of the receive data buffer AHB address to a particular value when the associated enable bits stored in this register [3:0] are set. Any changes to this register will be ignored while the DMA is currently processing a receive packet. It will only affect the next full packet to be written to external system memory.

11.1.47 ETH_RX_PTP_UNICAST

Description: PTP RX unicast IP destination address
Address: 0x404810D4
Offset: 0x10D4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_UNICAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_UNICAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_UNICAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_UNICAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_UNICAST	RW	RW	0	Unicast IP destination address. Used for detection of PTP frames on receive path.

11.1.48 ETH_TX_PTP_UNICAST

Description: PTP TX unicast IP destination address
Address: 0x404810D8
Offset: 0x10D8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDRESS_UNICAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDRESS_UNICAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDRESS_UNICAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDRESS_UNICAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADDRESS_UNICAST	RW	RW	0	Unicast IP destination address. Used for detection of PTP frames on transmit path.

11.1.49 ETH_TSU_NSEC_CMP

Description: TSU timer comparison value nanoseconds
Address: 0x404810DC
Offset: 0x10DC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARISON_NSEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARISON_NSEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		COMPARISON_NSEC [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:21	COMPARISON_NSEC	RW	RW	0	TSU timer comparison value (ns). Value is compared to the bits[45:24] of the TSU timer count value (upper 22 bits of nanosecond value).

11.1.50 ETH_TSU_SEC_CMP

Description: TSU timer comparison value seconds (31 to 0 bits)
Address: 0x404810E0
Offset: 0x10E0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARISON_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARISON_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARISON_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARISON_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COMPARISON_SEC	RW	RW	0	TSU timer comparison value (s). Value is compared to seconds value bits [31:0] of the TSU timer count value.

11.1.51 ETH_TSU_MSB_SEC_CMP

Description: TSU timer comparison value seconds (47 to 32 bits)
Address: 0x404810E4
Offset: 0x10E4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARISON_MSB_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARISON_MSB_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARISON_MSB_SEC	RW	RW	0	TSU timer comparison value (s). Value is compared to the top 16 bits (most significant 16-bits {47:32} of seconds value) of the TSU timer count value.

11.1.52 ETH_TSU_PTP_TX_MSB_SEC

Description: PTP Event Frame Transmitted Seconds Register (47 to 32 bits)
Address: 0x404810E8
Offset: 0x10E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_SECONDS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_SECONDS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMER_SECONDS	R	R	0	PTP Event Frame TX Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP transmit primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.53 ETH_TSU_PTP_RX_MSB_SEC

Description: PTP Event Frame Received Seconds Register (47 to 32 bits)
Address: 0x404810EC
Offset: 0x10EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_SECONDS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_SECONDS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMER_SECONDS	R	R	0	PTP Event Frame TX Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP receive primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.54 ETH_TSU_PEER_TX_MSB_SEC

Description: PTP Peer Event Frame Transmitted Seconds Register (47 to 32 bits)
Address: 0x404810F0
Offset: 0x10F0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_SECONDS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_SECONDS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMER_SECONDS	R	R	0	PTP Peer Event Frame TX Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP transmit peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.55 ETH_TSU_PEER_RX_MSB_SEC

Description: PTP Peer Event Frame Received Seconds Register (47 to 32 bits)
Address: 0x404810F4
Offset: 0x10F4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_SECONDS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_SECONDS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMER_SECONDS	R	R	0	PTP Peer Event Frame RX Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP receive peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.56 ETH_DPRAM_FILL_DBG

Description:	The fill levels for the TX & RX packet buffers can be read using this register, including the fill level for each queue in the TX direction.
Address:	0x404810F8
Offset:	0x10F8
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_TX_Q_FILL_LEVEL_SELECT [7:4]				None [3:1]			DMA_TX_RX_FILL_LEVEL_SELECT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_TX_RX_FILL_LEVEL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_TX_RX_FILL_LEVEL [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_TX_RX_FILL_LEVEL_SELECT	RW	RW	0	TX/RX Fill Level select - report the fill level for the TX or RX packet buffer.
4:7	DMA_TX_Q_FILL_LEVEL_SELECT	RW	RW	0	TX queue fill level select - select what TX queue to report fill levels for.
16:31	DMA_TX_RX_FILL_LEVEL	R	R	0	Fill Level - TX or RX packet buffer fill level, selected by the tx_q_fill_level_select and tx_rx_fill_level_select registers. Read this register to determine the fill level.

11.1.57 ETH_REVISION_REG

Description: This register indicates a Cadence module identification number and module revision. The value of this register is read only as defined by `gem\_revision\_reg\_value`

Address: 0x404810FC

Offset: 0x10FC

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x70109

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MODULE_REVISION [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MODULE_REVISION [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	MODULE_IDENTIFICATION_NUMBER [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	FIX_NUMBER [31:28]				MODULE_IDENTIFICATION_NUMBER [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MODULE_REVISION	R	R	265	Module revision - fixed value specific to the revision of the design which is incremented for each non-fix release of the IP.
16:27	MODULE_IDENTIFICATION_NUMBER	R	R	7	Module identification number - for the GEM, this value is fixed.
28:31	FIX_NUMBER	R	R	0	Fix number - incremented for fix releases.

11.1.58 ETH_OCTETS_TXED_BOTTOM

Description:	Octets Transmitted lower bits (31 to 0 bits)
Address:	0x40481100
Offset:	0x1100
Retention:	Not Retained
IsDeepSleep:	No
Comment:	These registers reset to zero on a read and stick at all ones when they count to their maximum value. They should be read frequently enough to prevent loss of data. In order to reduce overall design area, the statistics registers may be optionally removed in the configuration file if they are deemed unnecessary for a particular design. The receive statistics registers are only incremented when the receive enable bit is set in the network control register. The statistics registers optionally have a snapshot capability which, when exercised, will simultaneously store and clear the current values of all the statistics registers into a snapshot register set in order to allow a consistent set of statistics to be read by the processor. The snapshot is controlled using bit 13 of the network control register. The read snapshot control indicated by bit 14 of the network control register determines whether the processor reads the snapshot registers (logic 1) or the incrementing registers (logic 0). The default GEM configuration does not support the snapshot capability. See Parameterization section under Implementation Application Notes for an explanation of how to enable this function. All the statistics registers are read only. For test purposes they may be written by setting bit 7 (Write Enable) in the network control register. Setting bit 6 (increment statistics) in the network control register causes all the statistics registers to increment by one, again for test purposes. Once a statistics register has been read, it is automatically cleared. When reading the octets transmitted and octets received registers, bits 31:0 should be read prior to bits 47:32 to ensure reliable operation. The statistics register block contains the following registers. Octets Transmitted [31:0]
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_BOTTOM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_BOTTOM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_BOTTOM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_BOTTOM	RC	RC	0	Transmitted octets in frame without errors [31:0]. The number of octets transmitted in valid frames of any type. This counter is 48-bits, and is read through two registers. This count does not include octets from automatically generated pause frames.

11.1.59 ETH_OCTETS_TXED_TOP

Description: Octets Transmitted higher bits (47 to 32 bits)
Address: 0x40481104
Offset: 0x1104
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_TOP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_TOP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_TOP	RC	RC	0	Transmitted octets in frame without errors [47:32]. The number of octets transmitted in valid frames of any type. This counter is 48-bits, and is read through two registers. This count does not include octets from automatically generated pause frames.

11.1.60 ETH_FRAMES_TXED_OK

Description: Frames Transmitted
Address: 0x40481108
Offset: 0x1108
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_OK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_OK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_OK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_OK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_OK	RC	RC	0	Frames transmitted without error. A 32 bit register counting the number of frames successfully transmitted, i.e. no under run and not too many retries. Excludes pause frames.

11.1.61 ETH_BROADCAST_TXED

Description: Broadcast Frames Transmitted
Address: 0x4048110C
Offset: 0x110C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_BROADCAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_BROADCAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_BROADCAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_BROADCAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_BROADCAST	RC	RC	0	Broadcast frames transmitted without error. A 32 bit register counting the number of broadcast frames successfully transmitted without error, i.e. no under run and not too many retries. Excludes pause frames.

11.1.62 ETH_MULTICAST_TXED

Description: Multicast Frames Transmitted
Address: 0x40481110
Offset: 0x1110
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_MULTICAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_MULTICAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_MULTICAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_MULTICAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_MULTICAST	RC	RC	0	Multicast frames transmitted without error. A 32 bit register counting the number of multicast frames successfully transmitted without error, i.e. no under run and not too many retries. Excludes pause frames.

11.1.63 ETH_PAUSE_FRAMES_TXED

Description: Pause Frames Transmitted
Address: 0x40481114
Offset: 0x1114
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_PAUSE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_PAUSE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_PAUSE	RC	RC	0	Transmitted pause frames - a 16 bit register counting the number of pause frames transmitted. Only pause frames triggered by the register interface or through the external pause pins are counted as pause frames. Pause frames received through the external FIFO interface are counted in the frames transmitted counter.

11.1.64 ETH_FRAMES_TXED_64

Description: 64 Byte Frames Transmitted
Address: 0x40481118
Offset: 0x1118
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_64 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_64 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_64 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_64 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_64	RC	RC	0	64 byte frames transmitted without error. A 32 bit register counting the number of 64 byte frames successfully transmitted without error, i.e. no under run and not too many retries. Excludes pause frames.

11.1.65 ETH_FRAMES_TXED_65

Description: 65 to 127 Byte Frames Transmitted
Address: 0x4048111C
Offset: 0x111C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_65 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_65 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_65 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_65 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_65	RC	RC	0	65 to 127 byte frames transmitted without error. A 32 bit register counting the number of 65 to 127 byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.66 ETH_FRAMES_TXED_128

Description: 128 to 255 Byte Frames Transmitted
Address: 0x40481120
Offset: 0x1120
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_128 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_128 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_128 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_128 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_128	RC	RC	0	128 to 255 byte frames transmitted without error. A 32 bit register counting the number of 128 to 255 byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.67 ETH_FRAMES_TXED_256

Description: 256 to 511 Byte Frames Transmitted
Address: 0x40481124
Offset: 0x1124
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_256 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_256 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_256 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_256 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_256	RC	RC	0	256 to 511 byte frames transmitted without error. A 32 bit register counting the number of 256 to 511 byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.68 ETH_FRAMES_TXED_512

Description: 512 to 1023 Byte Frames Transmitted
Address: 0x40481128
Offset: 0x1128
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_512 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_512 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_512 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_512 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_512	RC	RC	0	512 to 1023 byte frames transmitted without error. A 32 bit register counting the number of 512 to 1023 byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.69 ETH_FRAMES_TXED_1024

Description: 1024 to 1518 Byte Frames Transmitted
Address: 0x4048112C
Offset: 0x112C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_1024 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_1024 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_1024 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_1024 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_1024	RC	RC	0	1024 to 1518 byte frames transmitted without error. A 32 bit register counting the number of 1024 to 1518 byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.70 ETH_FRAMES_TXED_1519

Description: Greater Than 1518 Byte Frames Transmitted
Address: 0x40481130
Offset: 0x1130
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_1519 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_1519 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_1519 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_1519 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_1519	RC	RC	0	Greater than 1518 byte frames transmitted without error. A 32 bit register counting the number of 1518 or above byte frames successfully transmitted without error, i.e. no under run and not too many retries.

11.1.71 ETH_TX_UNDERRUNS

Description: Transmit Under Runs
Address: 0x40481134
Offset: 0x1134
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_UN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_UN [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_UN	RC	RC	0	Transmit under runs - a 10 bit register counting the number of frames not transmitted due to a transmit under run. If this register is incremented then no other statistics register is incremented.

11.1.72 ETH_SINGLE_COLLISIONS

Description: Single Collision Frames. Presents in design but not support.
Address: 0x40481138
Offset: 0x1138
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT14 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT14 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						COUNT14 [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	COUNT14	RC	RC	0	Single collision frames - an 18 bit register counting the number of frames experiencing a single collision before being successfully transmitted, i.e. no under run.

11.1.73 ETH_MULTIPLE_COLLISIONS

Description: Multiple Collision Frames. Presents in design but not support.
Address: 0x4048113C
Offset: 0x113C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT15 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT15 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						COUNT15 [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	COUNT15	RC	RC	0	Multiple collision frames - an 18 bit register counting the number of frames experiencing between two and fifteen collisions prior to being successfully transmitted, i.e. no under run and not too many retries.

11.1.74 ETH_EXCESSIVE_COLLISIONS

Description: Excessive Collisions. Presents in design but not support.
Address: 0x40481140
Offset: 0x1140
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT16 [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT16	RC	RC	0	Excessive collisions - a 10 bit register counting the number of frames that failed to be transmitted because they experienced 16 collisions.

11.1.75 ETH_LATE_COLLISIONS

Description: Late Collisions. Presents in design but not support.
Address: 0x40481144
Offset: 0x1144
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT17 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT17 [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT17	RC	RC	0	Late collisions - a 10 bit register counting the number of late collision occurring after the slot time (512 bits) has expired. In 10/100 mode, late collisions are counted twice i.e. both as a collision and a late collision. In gigabit mode, a late collision causes the transmission to be aborted, thus the single and multi collision registers are not updated.

11.1.76 ETH_DEFERRED_FRAMES

Description: Deferred Transmission Frames. Presents in design but not support.
Address: 0x40481148
Offset: 0x1148
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT18 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT18 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						COUNT18 [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	COUNT18	RC	RC	0	Deferred transmission frames - an 18 bit register counting the number of frames experiencing deferral due to carrier sense being active on their first attempt at transmission. Frames involved in any collision are not counted nor are frames that experienced a transmit under run.

11.1.77 ETH_CRS_ERRORS

Description: Carrier Sense Errors. Presents in design but not support.
Address: 0x4048114C
Offset: 0x114C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT19 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT19 [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT19	RC	RC	0	Carrier sense errors - a 10 bit register counting the number of frames transmitted where carrier sense was not seen during transmission or where carrier sense was deasserted after being asserted in a transmit frame without collision (no under run). Only incremented in half duplex mode. The only effect of a carrier sense error is to increment this register. The behaviour of the other statistics registers is unaffected by the detection of a carrier sense error.

11.1.78 ETH_OCTETS_RXED_BOTTOM

Description: Octets Received (31 to 0 bits)
Address: 0x40481150
Offset: 0x1150
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_BOTTOM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_BOTTOM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_BOTTOM [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_BOTTOM [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_BOTTOM	RC	RC	0	Received octets in frame without errors [31:0]. The number of octets received in valid frames of any type. This counter is 48-bits and is read through two registers. This count does not include octets from pause frames, and is only incremented if the frame is successfully filtered.

11.1.79 ETH_OCTETS_RXED_TOP

Description: Octets Received (47 to 32 bits)
Address: 0x40481154
Offset: 0x1154
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_TOP [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_TOP [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_TOP	RC	RC	0	Received octets in frame without errors [47:32]. The number of octets received in valid frames of any type. This counter is 48-bits and is read through two registers. This count does not include octets from pause frames, and is only incremented if the frame is successfully filtered.

11.1.80 ETH_FRAMES_RXED_OK

Description: Frames Received
Address: 0x40481158
Offset: 0x1158
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_OK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_OK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_OK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_OK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_OK	RC	RC	0	Frames received without error. A 32 bit register counting the number of frames successfully received. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.81 ETH_BROADCAST_RXED

Description: Broadcast Frames Received
Address: 0x4048115C
Offset: 0x115C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_BROADCAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_BROADCAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_BROADCAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_BROADCAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_BROADCAST	RC	RC	0	Broadcast frames received without error. A 32 bit register counting the number of broadcast frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.82 ETH_MULTICAST_RXED

Description: Multicast Frames Received
Address: 0x40481160
Offset: 0x1160
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_MULTICAST [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_MULTICAST [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_MULTICAST [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_MULTICAST [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_MULTICAST	RC	RC	0	Multicast frames received without error. A 32 bit register counting the number of multicast frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.83 ETH_PAUSE_FRAMES_RXED

Description: Pause Frames Received
Address: 0x40481164
Offset: 0x1164
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_PAUSE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_PAUSE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_PAUSE	RC	RC	0	Received pause frames - a 16 bit register counting the number of pause frames received without error.

11.1.84 ETH_FRAMES_RXED_64

Description: 64 Byte Frames Received
Address: 0x40481168
Offset: 0x1168
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_64 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_64 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_64 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_64 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_64	RC	RC	0	64 byte frames received without error. A 32 bit register counting the number of 64 byte frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.85 ETH_FRAMES_RXED_65

Description: 65 to 127 Byte Frames Received
Address: 0x4048116C
Offset: 0x116C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_65 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_65 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_65 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_65 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_65	RC	RC	0	65 to 127 byte frames received without error. A 32 bit register counting the number of 65 to 127 byte frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.86 ETH_FRAMES_RXED_128

Description: 128 to 255 Byte Frames Received
Address: 0x40481170
Offset: 0x1170
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_128 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_128 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_128 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_128 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_128	RC	RC	0	128 to 255 byte frames received without error. A 32 bit register counting the number of 128 to 255 byte frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.87 ETH_FRAMES_RXED_256

Description: 256 to 511 Byte Frames Received
Address: 0x40481174
Offset: 0x1174
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_256 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_256 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_256 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_256 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_256	RC	RC	0	256 to 511 byte frames received without error. A 32 bit register counting the number of 256 to 511 byte frames successfully transmitted without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.88 ETH_FRAMES_RXED_512

Description: 512 to 1023 Byte Frames Received
Address: 0x40481178
Offset: 0x1178
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_512 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_512 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_512 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_512 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_512	RC	RC	0	512 to 1023 byte frames received without error. A 32 bit register counting the number of 512 to 1023 byte frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.89 ETH_FRAMES_RXED_1024

Description: 1024 to 1518 Byte Frames Received
Address: 0x4048117C
Offset: 0x117C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_1024 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_1024 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_1024 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_1024 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_1024	RC	RC	0	1024 to 1518 byte frames received without error. A 32 bit register counting the number of 1024 to 1518 byte frames successfully received without error. Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.90 ETH_FRAMES_RXED_1519

Description: 1519 to maximum Byte Frames Received
Address: 0x40481180
Offset: 0x1180
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_1519 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_1519 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNT_1519 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNT_1519 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNT_1519	RC	RC	0	1519 to maximum byte frames received without error. A 32 bit register counting the number of 1519 byte or above frames successfully received without error. Maximum frame size is determined by the network configuration register bit 8 (1536 maximum frame size) or bit 3 (jumbo frame size). Excludes pause frames, and is only incremented if the frame is successfully filtered.

11.1.91 ETH_UNDERSIZE_FRAMES

Description: Undersized Frames Received
Address: 0x40481184
Offset: 0x1184
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_UNDERSIZE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_UNDERSIZE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_UNDERSIZE	RC	RC	0	Undersize frames received - a 10 bit register counting the number of frames received less than 64 bytes in length (10/100 mode or gigabit mode, full duplex) that do not have either a CRC error or an alignment error. In gigabit mode, half duplex, this register counts either frames not conforming to the minimum slot time of 512 bytes or frames not conforming to the minimum frame size once bursting is active.

11.1.92 ETH_EXCESSIVE_RX_LENGTH

Description: Oversize Frames Received
Address: 0x40481188
Offset: 0x1188
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_OVERSIZE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_OVERSIZE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_OVERSIZE	RC	RC	0	Oversize frames received - a 10 bit register counting the number of frames received exceeding 1518 bytes (1536 bytes if bit 8 is set in network configuration register, 10,240 bytes if bit 3 is set in the network configuration register) in length but do not have either a CRC error, an alignment error nor a receive symbol error.

11.1.93 ETH_RX_JABBERS

Description: Jabbers Received
Address: 0x4048118C
Offset: 0x118C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_JABBERS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_JABBERS [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_JABBERS	RC	RC	0	Jabbers received - a 10 bit register counting the number of frames received exceeding 1518 bytes (1536 if bit 8 set in network configuration register, 10,240 bytes if bit 3 is set in the network configuration register) in length and have either a CRC error, an alignment error or a receive symbol error.

11.1.94 ETH_FCS_ERRORS

Description: Frame Check Sequence Errors
Address: 0x40481190
Offset: 0x1190
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_FCS_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_FCS_ERR [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_FCS_ERR	RC	RC	0	Frame check sequence errors - a 10 bit register counting frames that are an integral number of bytes, have bad CRC and are between 64 and 1518 bytes in length (1536 if bit 8 set in network configuration register, 10,240 bytes if bit 3 is set in the network configuration register). This register is also incremented if a symbol error is detected and the frame is of valid length and has an integral number of bytes. This register is incremented for a frame with bad FCS, regardless of whether it is copied to memory due to ignore FCS mode being enabled in bit 26 of the network configuration register.

11.1.95 ETH_RX_LENGTH_ERRORS

Description: Length Field Frame Errors
Address: 0x40481194
Offset: 0x1194
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_LENGTH_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_LENGTH_ERR [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_LENGTH_ERR	RC	RC	0	Length field frame errors - this 10-bit register counts the number of frames received that have a measured length shorter than that extracted from the length field (bytes 13 and 14). This condition is only counted if the value of the length field is less than 0x0600, the frame is not of excessive length and checking is enabled through bit 16 of the network configuration register.

11.1.96 ETH_RX_SYMBOL_ERRORS

Description: Receive Symbol Errors
Address: 0x40481198
Offset: 0x1198
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_SYMBOL_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_SYMBOL_ERR [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_SYMBOL_ERR	RC	RC	0	Receive symbol errors - a 10-bit register counting the number of frames that had rx_er asserted during reception. For 10/100 mode symbol errors are counted regardless of frame length checks. For gigabit mode the frame must satisfy slot time requirements in order to count a symbol error. Additionally, in gigabit half duplex mode, carrier extension errors are also recorded. Receive symbol errors will also be counted as an FCS or alignment error if the frame is between 64 and 1518 bytes (1536 bytes if bit 8 is set in the network configuration register, 10240 bytes if bit 3 is set in the network configuration register). If the frame is larger it will be recorded as a jabber error.

11.1.97 ETH_ALIGNMENT_ERRORS

Description: Alignment Errors
Address: 0x4048119C
Offset: 0x119C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_ALIGNMENT_ERROR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_ALIGNMENT_ERROR [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_ALIGNMENT_ERROR	RC	RC	0	Alignment errors - a 10 bit register counting frames that are not an integral number of bytes long and have bad CRC when their length is truncated to an integral number of bytes and are between 64 and 1518 bytes in length (1536 if bit 8 set in network configuration register, 10,240 bytes if bit 3 is set in the network configuration register). This register is also incremented if a symbol error is detected and the frame is of valid length and does not have an integral number of bytes.

11.1.98 ETH_RX_RESOURCE_ERRORS

Description: Receive Resource Errors
Address: 0x404811A0
Offset: 0x11A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_RESOURCE_ERR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	COUNT_RESOURCE_ERR [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						COUNT_RESOURCE_ERR [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	COUNT_RESOURCE_ERR	RC	RC	0	Receive resource errors - an 18 bit register counting the number of frames that were successfully received by the MAC (correct address matched frame and adequate slot time) but could not be copied to memory because no receive buffer was available. This occurs when the GEM reads a buffer descriptor with its ownership (or used) bit set.

11.1.99 ETH_RX_OVERRUNS

Description: Receive Overruns
Address: 0x404811A4
Offset: 0x11A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_OVERRUN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						COUNT_OVERRUN [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	COUNT_OVERRUN	RC	RC	0	Receive overruns - a 10 bit register counting the number of frames that are address recognized but were not copied to memory due to a receive overrun.

11.1.100 ETH_RX_IP_CHK_ERRORS

Description: IP Header Checksum Errors
Address: 0x404811A8
Offset: 0x11A8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_IPCK_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	COUNT_IPCK_ERR	RC	RC	0	IP header checksum errors - an 8-bit register counting the number of frames discarded due to an incorrect IP header checksum, but are between 64 and 1518 bytes (1536 bytes if bit 8 is set in the network configuration register or 10240 bytes if bit 3 is in the network configuration register) and do not have a CRC error, an alignment error, nor a symbol error.

11.1.101 ETH_RX_TCP_CHK_ERRORS

Description: TCP Checksum Errors
Address: 0x404811AC
Offset: 0x11AC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_TCPCK_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	COUNT_TCPCK_ERR	RC	RC	0	TCP checksum errors - an 8-bit register counting the number of frames discarded due to an incorrect TCP checksum, but are between 64 and 1518 bytes (1536 bytes if bit 8 is set in the network configuration register or 10240 bytes if bit 3 is in the network configuration register) and do not have a CRC error, an alignment error, nor a symbol error.

11.1.102 ETH_RX_UDP_CHK_ERRORS

Description: UDP Checksum Errors
Address: 0x404811B0
Offset: 0x11B0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_UDPCK_ERR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	COUNT_UDPCK_ERR	RC	RC	0	UDP checksum errors - an 8-bit register counting the number of frames discarded due to an incorrect UDP checksum, but are between 64 and 1518 bytes (1536 bytes if bit 8 is set in the network configuration register or 10240 bytes if bit 3 is in the network configuration register) and do not have a CRC error, an alignment error, nor a symbol error.

11.1.103 ETH_AUTO_FLUSHED_PKTS

Description: Receive DMA Flushed Packets
Address: 0x404811B4
Offset: 0x11B4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_FLUSHED [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_FLUSHED [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_FLUSHED	RC	RC	0	Flushed RX packets counter. A 16 bit register counting the number of frames that have been flushed from the receive SRAM based packet buffer due to one of the following reasons .1. When partial store and forward mode is enabled or bit 24 of the DMA configuration register is enabled, a packet is received while there is no AMBA (AXI/AHB) resource. 2. When partial store and forward mode is enabled and an AMBA (AXI/AHB) error is encountered while writing the packet data to external memory. When bit 18 of the network control register(software action to flush a packet from the head of the PBUF queue) is pulsed and the GEM DMA is not currently busy.

11.1.104 ETH_TSU_TIMER_INCR_SUB_NSEC

Description: 1588 Timer Increment Register sub nsec
Address: 0x404811BC
Offset: 0x11BC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUB_NS_INCR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SUB_NS_INCR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SUB_NS_INCR_LSB [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	SUB_NS_INCR	RW	RW	0	These are the most significant bits [23:8] of the sub-ns value by which the 1588 timer will be incremented each clock cycle. 24 bits of sub nanosecond precision gives resolution of approximately 5.86E-17 seconds (16 bits gives 15.2 femtoseconds).
24:31	SUB_NS_INCR_LSB	RW	RW	0	These are the least significant bits [7:0] of the sub-ns value by which the 1588 timer will be incremented each clock cycle.

11.1.105 ETH_TSU_TIMER_MSB_SEC

Description: 1588 Timer Seconds Register (47 to 32 bits)
Address: 0x404811C0
Offset: 0x11C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_MSB_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_MSB_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMER_MSB_SEC	RW	RW	0	TSU timer value (s). Most significant 16 bits of seconds timer count. The register is writeable. The 48-bit counter increments by one when the 1588 nanoseconds counter counts to one second. It may also be incremented or decremented when the timer adjust register is written (if decremented from zero the 48-bit combined count would roll back to 0xFFFFFFFF). Note: The value of this register is used only when the lower 32 bit register is written to. This is to ensure a single update of the 48 bit seconds value

11.1.106 ETH_TSU_STROBE_MSB_SEC

Description: 1588 Timer Sync Strobe Seconds Register (47 to 32 bits)
Address: 0x404811C4
Offset: 0x11C4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STROBE_MSB_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	STROBE_MSB_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	STROBE_MSB_SEC	R	R	0	1588 Timer Sync Strobe Seconds. The most significant 16-bit value of the Timer Seconds register captured when gem_tsu_ms and gem_tsu_inc_ctrl are zero.

11.1.107 ETH_TSU_STROBE_SEC

Description: 1588 Timer Sync Strobe Seconds Register (31 to 0 bits)
Address: 0x404811C8
Offset: 0x11C8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STROBE_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	STROBE_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	STROBE_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	STROBE_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	STROBE_SEC	R	R	0	1588 Timer Sync Strobe Seconds. The lowest significant 32-bit value of the Timer Seconds register captured when gem_tsu_ms and gem_tsu_inc_ctrl are zero.

11.1.108 ETH_TSU_STROBE_NSEC

Description: 1588 Timer Sync Strobe Nanoseconds Register
Address: 0x404811CC
Offset: 0x11CC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STROBE_NSEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	STROBE_NSEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	STROBE_NSEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		STROBE_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	STROBE_NSEC	R	R	0	1588 Timer Sync Strobe Nanoseconds. The value of the Timer Nanoseconds register captured when gem_tsu_ms and gem_tsu_inc_ctrl are zero.

11.1.109 ETH_TSU_TIMER_SEC

Description: 1588 Timer Seconds Register (31 to 0 bits)
Address: 0x404811D0
Offset: 0x11D0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_SEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TIMER_SEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TIMER_SEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	TIMER_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIMER_SEC	RW	RW	0	1588 Timer Seconds Register. TSU timer value (s). Least significant 32 bits of seconds timer count. This register is writeable. The 48-bit counter increments by one when the 1588 nanoseconds counter counts to one second. It may also be incremented or decremented when the timer adjust register is written (if decremented from zero the 48-bit combined count would roll back to 0xFFFFFFFFFFFF).

11.1.110 ETH_TSU_TIMER_NSEC

Description: 1588 Timer Nanoseconds Register
Address: 0x404811D4
Offset: 0x11D4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_NSEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TIMER_NSEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TIMER_NSEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TIMER_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	TIMER_NSEC	RW	RW	0	Timer count in nanoseconds. This register is writeable. It can also be adjusted by writes to the 1588 timer adjust register. It increments by the value of the 1588 timer increment register each clock cycle (if this register is close to zero and a write to the timer adjust register causes a decrement the seconds register will be decremented if necessary and the nanoseconds register will roll back to 9999999xx(decimal)).

11.1.111 ETH_TSU_TIMER_ADJUST

Description: This register is used to adjust the value of the timer in the TSU. It allows an integral number of nanoseconds to be added or subtracted from the timer in a one-off operation. This register returns all zeroes when read.

Address: 0x404811D8

Offset: 0x11D8

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INCREMENT_VALUE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	INCREMENT_VALUE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	INCREMENT_VALUE [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADD _SUBTR ACT [31:31]	None [30:30]	INCREMENT_VALUE [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	INCREMENT_VALUE	W	W	0	Timer increment value. The number of nanoseconds to increment or decrement the 1588 timer nanoseconds register. If necessary the 1588 seconds register will be incremented or decremented.
31	ADD_SUBTRACT	W	W	0	Write as one to subtract from the 1588 timer. Write as zero to add to it.

11.1.112 ETH_TSU_TIMER_INCR

Description: 1588 Timer Increment Register
Address: 0x404811DC
Offset: 0x11DC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NS_INCREMENT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ALT_NS_INCR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	NUM_INCS [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	NS_INCREMENT	RW	RW	0	A count of nanoseconds by which the 1588 timer nanoseconds register will be incremented each clock cycle. These are the most significant 8 bits of the 32 bit timer_increment counter. The tsu_timer_incr_sub_nsec register holds the least significant 24 bits of the increment.
8:15	ALT_NS_INCR	RW	RW	0	Alternative nanoseconds count. Alternative count of nanoseconds by which the 1588 timer nanoseconds register will be incremented each clock cycle.
16:23	NUM_INCS	RW	RW	0	Number of incs before alt inc. The number of increments after which the alternative increment is used.

11.1.113 ETH_TSU_PTP_TX_SEC

Description: PTP Event Frame Transmitted Seconds Register (31 to 0 bits)
Address: 0x404811E0
Offset: 0x11E0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PTP_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_PTP_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIMER_PTP_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TIMER_PTP_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIMER_PTP_SEC	R	R	0	PTP Event Frame Transmitted Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP transmit primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.114 ETH_TSU_PTP_TX_NSEC

Description: PTP Event Frame Transmitted Nanoseconds Register
Address: 0x404811E4
Offset: 0x11E4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PTP_NSEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TIMER_PTP_NSEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TIMER_PTP_NSEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TIMER_PTP_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	TIMER_PTP_NSEC	R	R	0	PTP Event Frame Transmitted Nanoseconds. The register is updated with the value that the 1588 timer nanoseconds register held when the SFD of a PTP transmit primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.115 ETH_TSU_PTP_RX_SEC

Description: PTP Event Frame Received Seconds Register (31 to 0 bits)
Address: 0x404811E8
Offset: 0x11E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PTP_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_PTP_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIMER_PTP_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TIMER_PTP_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIMER_PTP_SEC	R	R	0	PTP Event Frame Received Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP receive primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.116 ETH_TSU_PTP_RX_NSEC

Description: PTP Event Frame Received Nanoseconds Register
Address: 0x404811EC
Offset: 0x11EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PTP_NSEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_PTP_NSEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIMER_PTP_NSEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TIMER_PTP_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	TIMER_PTP_NSEC	R	R	0	PTP Event Frame Received Nanoseconds. The register is updated with the value that the 1588 timer nanoseconds register held when the SFD of a PTP receive primary event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP sync or delay_req frame. An interrupt is issued when the register is updated.

11.1.117 ETH_TSU_PEER_TX_SEC

Description: PTP Peer Event Frame Transmitted Seconds Register (31 to 0 bits)
Address: 0x404811F0
Offset: 0x11F0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PEER_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_PEER_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIMER_PEER_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TIMER_PEER_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIMER_PEER_SEC	R	R	0	PTP Peer Event Frame Received Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP transmit peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.118 ETH_TSU_PEER_TX_NSEC

Description: PTP Peer Event Frame Transmitted Nanoseconds Register
Address: 0x404811F4
Offset: 0x11F4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PEER_NSEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TIMER_PEER_NSEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TIMER_PEER_NSEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TIMER_PEER_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	TIMER_PEER_NSEC	R	R	0	PTP Peer Event Frame Transmitted Nanoseconds. The register is updated with the value that the 1588 timer nanoseconds register held when the SFD of a PTP transmit peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.119 ETH_TSU_PEER_RX_SEC

Description: PTP Peer Event Frame Received Seconds Register (31 to 0 bits)
Address: 0x404811F8
Offset: 0x11F8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PEER_SEC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMER_PEER_SEC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TIMER_PEER_SEC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TIMER_PEER_SEC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TIMER_PEER_SEC	R	R	0	PTP Peer Event Frame Received Seconds. The register is updated with the value that the 1588 timer seconds register held when the SFD of a PTP receive peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.120 ETH_TSU_PEER_RX_NSEC

Description: PTP Peer Event Frame Received Nanoseconds Register
Address: 0x404811FC
Offset: 0x11FC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMER_PEER_NSEC [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	TIMER_PEER_NSEC [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	TIMER_PEER_NSEC [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		TIMER_PEER_NSEC [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:29	TIMER_PEER_NSEC	R	R	0	PTP Peer Event Frame Received Nanoseconds. The register is updated with the value that the 1588 timer nanoseconds register held when the SFD of a PTP receive peer event crosses the MII interface. The actual update occurs when the GEM recognizes the frame as a PTP pdelay_req or pdelay_resp frame. An interrupt is issued when the register is updated.

11.1.121 ETH_PCS_CONTROL

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481200
Offset: 0x1200
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.122 ETH_PCS_STATUS

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481204
Offset: 0x1204
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.123 ETH_PCS_AN_ADV

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481210
Offset: 0x1210
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.124 ETH_PCS_AN_LP_BASE

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481214
Offset: 0x1214
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.125 ETH_PCS_AN_EXP

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481218
Offset: 0x1218
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.126 ETH_PCS_AN_NP_TX

Description: Not presents. Access to the register returns AHB error.
Address: 0x4048121C
Offset: 0x121C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.127 ETH_PCS_AN_LP_NP

Description: Not presents. Access to the register returns AHB error.
Address: 0x40481220
Offset: 0x1220
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.128 ETH_PCS_AN_EXT_STATUS

Description: Not presents. Access to the register returns AHB error.
Address: 0x4048123C
Offset: 0x123C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.129 ETH_TX_PAUSE_QUANTUM1

Description: Transmit Pause Quantum Register 1
Address: 0x40481260
Offset: 0x1260
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QUANTUM_P2 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	QUANTUM_P2 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	QUANTUM_P3 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	QUANTUM_P3 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	QUANTUM_P2	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 2.
16:31	QUANTUM_P3	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 3.

11.1.130 ETH_TX_PAUSE_QUANTUM2

Description: Transmit Pause Quantum Register 2
Address: 0x40481264
Offset: 0x1264
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QUANTUM_P4 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	QUANTUM_P4 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	QUANTUM_P5 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	QUANTUM_P5 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	QUANTUM_P4	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 4.
16:31	QUANTUM_P5	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 5.

11.1.131 ETH_TX_PAUSE_QUANTUM3

Description: Transmit Pause Quantum Register 3
Address: 0x40481268
Offset: 0x1268
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	QUANTUM_P6 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	QUANTUM_P6 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	QUANTUM_P7 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	QUANTUM_P7 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	QUANTUM_P6	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 6.
16:31	QUANTUM_P7	RW	RW	65535	Transmit pause quantum - written with the pause quantum value for pause frame transmission of priority 7.

11.1.132 ETH_RX_LPI

Description: Received LPI transitions
Address: 0x40481270
Offset: 0x1270
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_LPI [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_LPI [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_LPI	RC	RC	0	Count of RX LPI transitions. A count of the number of times there is a transition from receiving normal idle to receiving low power idle. Cleared on read.

11.1.133 ETH_RX_LPI_TIME

Description: Received LPI time
Address: 0x40481274
Offset: 0x1274
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LPI_TIME [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	LPI_TIME [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	LPI_TIME [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	LPI_TIME	RC	RC	0	Time in LPI. This register increments once every 16 pclk cycles when the LPI indication bit 20 is set in the receive configuration register. Cleared on read.

11.1.134 ETH_TX_LPI

Description: Transmit LPI transitions
Address: 0x40481278
Offset: 0x1278
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT_LPI [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_LPI [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COUNT_LPI	RC	RC	0	Count of LPI transmissions. A count of the number of times the enable LPI transmission bit 20 goes from low to high in the transmit control register.

11.1.135 ETH_TX_LPI_TIME

Description: Transmit LPI time
Address: 0x4048127C
Offset: 0x127C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LPI_TIME [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LPI_TIME [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LPI_TIME [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	LPI_TIME	RC	RC	0	Time in LPI. This register increments once every 16 pclk cycles when the enable LPI transmission bit 20 is set in the transmit control register. Cleared on read.

11.1.136 ETH_DESIGNCFG_DEBUG1

Description:	The GEM_GXL(3PIP) has many parameterisation options to configure the IP during compilation stage. This is achieved using Verilog define compiler directives in an include file called mxeth_defs.v.
Address:	0x40481280
Offset:	0x1280
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x508503

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	EXT_FIFO_INTERFACE [6:6]	RESERVED_5 [5:5]	INT_LOOPBACK [4:4]	RESERVED_2 [3:2]	EXCLUDE_QBV [1:1]	NO_PCS [0:0]	

Bits	15	14	13	12	11	10	9	8
Name		USER_OUT_WIDTH [14:10]					USER_IO [9:9]	RESERVED_8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	IRQ_READ_CLEAR [23:23]	NO_SNAPSHOT [22:22]	NO_STATS [21:21]	RESERVED_20 [20:20]	USER_IN_WIDTH [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	AXI_CACHE_VALUE [31:28]				DMA_BUS_WIDTH [27:25]			EXCLUDE_CBS [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	NO_PCS	R	R	1	Takes the value of the `gem_no_pcs` DEFINE
1	EXCLUDE_QBV	R	R	1	Takes the value of the `gem_exclude_qbv` DEFINE
2:3	RESERVED_2	R	R	0	Reserved, read as 0, ignored on write.
4	INT_LOOPBACK	R	R	0	Takes the value of the `gem_int_loopback` DEFINE
5	RESERVED_5	R	R	0	Reserved, read as 0, ignored on write
6	EXT_FIFO_INTERFACE	R	R	0	Takes the value of the `gem_ext_fifo_interface` DEFINE
7	RESERVED_7	R	R	0	Reserved, read as 0, ignored on write
8	RESERVED_8	R	R	1	Reserved, read as 1, ignored on write
9	USER_IO	R	R	0	Takes the value of the `gem_user_io` DEFINE
10:14	USER_OUT_WIDTH	R	R	1	Takes the value of the `gem_user_out_width` DEFINE if `gem_user_io` is set. If `gem_user_io` is not set, the value is 0x01
15:19	USER_IN_WIDTH	R	R	1	Takes the value of the `gem_user_in_width` DEFINE if `gem_user_io` is set. If `gem_user_io` is not set, the value is 0x01
20	RESERVED_20	R	R	1	Reserved, read as 1, ignored on write
21	NO_STATS	R	R	0	Takes the value of the `gem_no_stats` DEFINE
22	NO_SNAPSHOT	R	R	1	Takes the value of the `gem_no_snapshot` DEFINE
23	IRQ_READ_CLEAR	R	R	0	Takes the value of the `gem_irq_read_clear` DEFINE
24	EXCLUDE_CBS	R	R	0	Takes the value of the `gem_exclude_cbs` DEFINE

Bits	Name	SW	HW	Default or Enum	Description
25:27	DMA_BUS_WIDTH	R	R	AXI _MASTER _PRESENT+ 1	Takes the value of bits 7:5 of the `gem_dma_bus_width` DEFINE. So if the define is set to decimal 64 this will return binary 010.
28:31	AXI_CACHE_VALUE	R	R	0	Takes the value of the `gem_axi_cache_value` DEFINE

11.1.137 ETH_DESIGNCFG_DEBUG2

Description: Design Configuration Register 2
Address: 0x40481284
Offset: 0x1284
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0xA6310600

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	JUMBO_MAX_LENGTH [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		JUMBO_MAX_LENGTH [13:8]					

Bits	23	22	21	20	19	18	17	16
Name			TX_PKT_BUFFER [21:21]	RX_PKT_BUFFER [20:20]	HPROT_VALUE [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	SPRAM [31:31]	AXI [30:30]	TX_PBUF_ADDR [29:26]				RX_PBUF_ADDR [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:13	JUMBO_MAX_LENGTH	R	R	1536	Takes the value of the `gem_jumbo_max_length` DEFINE
16:19	HPROT_VALUE	R	R	1	Takes the value of the `gem_hprot_value` DEFINE
20	RX_PKT_BUFFER	R	R	1	Takes the value of the `gem_rx_pkt_buffer` DEFINE
21	TX_PKT_BUFFER	R	R	1	Takes the value of the `gem_tx_pkt_buffer` DEFINE
22:25	RX_PBUF_ADDR	R	R	8	Takes the value of the `gem_rx_pbuf_addr` DEFINE
26:29	TX_PBUF_ADDR	R	R	9	Takes the value of the `gem_tx_pbuf_addr` DEFINE
30	AXI	R	R	AXI_MASTER_PRESENT	Takes the value of the `gem_axi` DEFINE
31	SPRAM	R	R	1	Takes the value of the `gem_spram` DEFINE

11.1.138 ETH_DESIGNCFG_DEBUG3

Description: Design Configuration Register 3
Address: 0x40481288
Offset: 0x1288
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x4000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		NUM_SPEC_ADD_FILTERS [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
24:29	NUM_SPEC_ADD_FILTERS	R	R	4	Takes the value of the `num_spec_add_filters` DEFINE

11.1.139 ETH_DESIGNCFG_DEBUG4

Description: Design Configuration Register 4
Address: 0x4048128C
Offset: 0x128C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Unused, read zero - reserved for `gem_tx_fifo_size` DEFINE in internal FIFO mode

11.1.140 ETH_DESIGNCFG_DEBUG5

Description: Design Configuration Register 5
Address: 0x40481290
Offset: 0x1290
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x518E3744

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TX_FIFO_CNT_WIDTH [7:4]				RX_FIFO_CNT_WIDTH [3:0]			

Bits	15	14	13	12	11	10	9	8
Name		MDC_CLOCK_DIV [14:12]			DMA_BUS_WIDTH_DEF [11:10]		PHY_IDENT [9:9]	TSU [8:8]

Bits	23	22	21	20	19	18	17	16
Name					TX_PBUF_SIZE_DEF [19:19]	RX_PBUF_SIZE_DEF [18:17]		ENDIAN_SWAP_DEF [16:16]

Bits	31	30	29	28	27	26	25	24
Name	AXI_PROT_VALUE [31:29]			TSU_CLK [28:28]	RX_BUFFER_LENGTH_DEF [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	RX_FIFO_CNT_WIDTH	R	R	4	Takes the value of the `gem_rx_fifo_cnt_width` DEFINE
4:7	TX_FIFO_CNT_WIDTH	R	R	4	Takes the value of the `gem_tx_fifo_cnt_width` DEFINE
8	TSU	R	R	1	Takes the value of the `gem_tsu` DEFINE
9	PHY_IDENT	R	R	1	Takes the value of the `gem_phy_ident` DEFINE
10:11	DMA_BUS_WIDTH_DEF	R	R	1	Takes the value of the `gem_dma_bus_width_def` DEFINE
12:14	MDC_CLOCK_DIV	R	R	3	Takes the value of the `gem_mdc_clock_div` DEFINE
15:16	ENDIAN_SWAP_DEF	R	R	0	Takes the value of the `gem_endian_swap_def` DEFINE
17:18	RX_PBUF_SIZE_DEF	R	R	3	Takes the value of the `gem_rx_pbuf_size_def` DEFINE
19	TX_PBUF_SIZE_DEF	R	R	1	Takes the value of the `gem_tx_pbuf_size_def` DEFINE
20:27	RX_BUFFER_LENGTH_DEF	R	R	24	Takes the value of the `gem_rx_buffer_length_def` DEFINE
28	TSU_CLK	R	R	1	Takes the value of the `gem_tsu_clk` DEFINE
29:31	AXI_PROT_VALUE	R	R	2	Takes the value of the `gem_axi_prot_value` DEFINE

11.1.141 ETH_DESIGNCFG_DEBUG6

Description: Design Configuration Register 6
Address: 0x40481294
Offset: 0x1294
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x3020006

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_PRIORITY_QUEUE7 [7:7]	DMA_PRIORITY_QUEUE6 [6:6]	DMA_PRIORITY_QUEUE5 [5:5]	DMA_PRIORITY_QUEUE4 [4:4]	DMA_PRIORITY_QUEUE3 [3:3]	DMA_PRIORITY_QUEUE2 [2:2]	DMA_PRIORITY_QUEUE1 [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_PRIORITY_QUEUE15 [15:15]	DMA_PRIORITY_QUEUE14 [14:14]	DMA_PRIORITY_QUEUE13 [13:13]	DMA_PRIORITY_QUEUE12 [12:12]	DMA_PRIORITY_QUEUE11 [11:11]	DMA_PRIORITY_QUEUE10 [10:10]	DMA_PRIORITY_QUEUE9 [9:9]	DMA_PRIORITY_QUEUE8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	DMA_ADDR_WIDTH_IS_64B [23:23]	HOST_IF_SOFT_SELECT [22:22]	TX_ADD_FIFO [21:21]	EXT_TSU_TIMER [20:20]	TX_PBUF_QUEUE_SEGMENT_SIZE [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				PBUF_LSO [27:27]	PBUF_RSC [26:26]	PBUF_CUTTHRU [25:25]	PFC_MULTI_QUANTUM [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	DMA_PRIORITY_QUEUE1	R	R	1	Takes the value of the `dma_priority_queue1` DEFINE
2	DMA_PRIORITY_QUEUE2	R	R	1	Takes the value of the `dma_priority_queue2` DEFINE
3	DMA_PRIORITY_QUEUE3	R	R	0	Takes the value of the `dma_priority_queue3` DEFINE
4	DMA_PRIORITY_QUEUE4	R	R	0	Takes the value of the `dma_priority_queue4` DEFINE
5	DMA_PRIORITY_QUEUE5	R	R	0	Takes the value of the `dma_priority_queue5` DEFINE
6	DMA_PRIORITY_QUEUE6	R	R	0	Takes the value of the `dma_priority_queue6` DEFINE
7	DMA_PRIORITY_QUEUE7	R	R	0	Takes the value of the `dma_priority_queue7` DEFINE
8	DMA_PRIORITY_QUEUE8	R	R	0	Takes the value of the `dma_priority_queue8` DEFINE
9	DMA_PRIORITY_QUEUE9	R	R	0	Takes the value of the `dma_priority_queue9` DEFINE
10	DMA_PRIORITY_QUEUE10	R	R	0	Takes the value of the `dma_priority_queue10` DEFINE
11	DMA_PRIORITY_QUEUE11	R	R	0	Takes the value of the `dma_priority_queue11` DEFINE

Bits	Name	SW	HW	Default or Enum	Description
12	DMA_PRIORITY_QUEUE12	R	R	0	Takes the value of the `dma_priority_queue12 DEFINE
13	DMA_PRIORITY_QUEUE13	R	R	0	Takes the value of the `dma_priority_queue13 DEFINE
14	DMA_PRIORITY_QUEUE14	R	R	0	Takes the value of the `dma_priority_queue14 DEFINE
15	DMA_PRIORITY_QUEUE15	R	R	0	Takes the value of the `dma_priority_queue15 DEFINE
16:19	TX_PBUF_QUEUE_SEGMENT_SIZE	R	R	2	Takes the value of the `gem_tx_pbuf_queue_segment_size DEFINE
20	EXT_TSU_TIMER	R	R	0	Takes the value of the `gem_ext_tsu_timer DEFINE
21	TX_ADD_FIFO_IF	R	R	0	Takes the value of the `gem_tx_add_fifo_if DEFINE
22	HOST_IF_SOFT_SELECT	R	R	0	Takes the value of the `gem_host_if_soft_select DEFINE
23	DMA_ADDR_WIDTH_IS_64B	R	R	0	Takes the value of the `gem_dma_addr_width_is_64b DEFINE
24	PFC_MULTI_QUANTUM	R	R	1	Takes the value of the `gem_pfc_multi_quantum DEFINE
25	PBUF_CUTTHRU	R	R	1	Takes the value of the `gem_pbuf_cutthru DEFINE
26	PBUF_RSC	R	R	0	Takes the value of the `gem_pbuf_rsc DEFINE
27	PBUF_LSO	R	R	0	Takes the value of the `gem_pbuf_lso DEFINE

11.1.142 ETH_DESIGNCFG_DEBUG7

Description: Design Configuration Register 7
Address: 0x40481298
Offset: 0x1298
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	X_PBUF_NUM_SEGMENTS_Q1 [7:4]				X_PBUF_NUM_SEGMENTS_Q0 [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	X_PBUF_NUM_SEGMENTS_Q3 [15:12]				X_PBUF_NUM_SEGMENTS_Q2 [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	X_PBUF_NUM_SEGMENTS_Q5 [23:20]				X_PBUF_NUM_SEGMENTS_Q4 [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	X_PBUF_NUM_SEGMENTS_Q7 [31:28]				X_PBUF_NUM_SEGMENTS_Q6 [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	X_PBUF_NUM_SEGMENTS_Q0	R	R	1	Takes the value of the `gem_tx_pbuf_num_segments_q0 DEFINE
4:7	X_PBUF_NUM_SEGMENTS_Q1	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q1 DEFINE
8:11	X_PBUF_NUM_SEGMENTS_Q2	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q2 DEFINE
12:15	X_PBUF_NUM_SEGMENTS_Q3	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q3 DEFINE
16:19	X_PBUF_NUM_SEGMENTS_Q4	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q4 DEFINE
20:23	X_PBUF_NUM_SEGMENTS_Q5	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q5 DEFINE
24:27	X_PBUF_NUM_SEGMENTS_Q6	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q6 DEFINE
28:31	X_PBUF_NUM_SEGMENTS_Q7	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q7 DEFINE

11.1.143 ETH_DESIGNCFG_DEBUG8

Description: Design Configuration Register 8
Address: 0x4048129C
Offset: 0x129C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x10100820

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	NUM_SCR2_COMPARE_REGS [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	NUM_SCR2_ETHTYPE_REGS [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	NUM_TYPE2_SCREENERS [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	NUM_TYPE1_SCREENERS [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	NUM_SCR2_COMPARE_REGS	R	R	32	Takes the value of the `num_scr2_compare_regs` DEFINE
8:15	NUM_SCR2_ETHTYPE_REGS	R	R	8	Takes the value of the `num_scr2_ethtype_regs` DEFINE
16:23	NUM_TYPE2_SCREENERS	R	R	16	Takes the value of the `num_type2_screensers` DEFINE
24:31	NUM_TYPE1_SCREENERS	R	R	16	Takes the value of the `num_type1_screensers` DEFINE

11.1.144 ETH_DESIGNCFG_DEBUG9

Description: Design Configuration Register 9
Address: 0x404812A0
Offset: 0x12A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TX_PBUF_NUM_SEGMENTS_Q9 [7:4]				TX_PBUF_NUM_SEGMENTS_Q8 [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	TX_PBUF_NUM_SEGMENTS_Q11 [15:12]				TX_PBUF_NUM_SEGMENTS_Q10 [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	TX_PBUF_NUM_SEGMENTS_Q13 [23:20]				TX_PBUF_NUM_SEGMENTS_Q12 [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	TX_PBUF_NUM_SEGMENTS_Q15 [31:28]				TX_PBUF_NUM_SEGMENTS_Q14 [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TX_PBUF_NUM_SEGMENTS_Q8	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q8 DEFINE
4:7	TX_PBUF_NUM_SEGMENTS_Q9	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q9 DEFINE
8:11	TX_PBUF_NUM_SEGMENTS_Q10	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q10 DEFINE
12:15	TX_PBUF_NUM_SEGMENTS_Q11	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q11 DEFINE
16:19	TX_PBUF_NUM_SEGMENTS_Q12	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q12 DEFINE
20:23	TX_PBUF_NUM_SEGMENTS_Q13	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q13 DEFINE
24:27	TX_PBUF_NUM_SEGMENTS_Q14	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q14 DEFINE
28:31	TX_PBUF_NUM_SEGMENTS_Q15	R	R	0	Takes the value of the `gem_tx_pbuf_num_segments_q15 DEFINE

11.1.145 ETH_DESIGNCFG_DEBUG10

Description: Design Configuration Register 10
Address: 0x404812A4
Offset: 0x12A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x4411111

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	AXI_TX_DESCR_WR_BUFF_BITS [7:4]				AXI_RX_DESCR_WR_BUFF_BITS [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	AXI_TX_DESCR_RD_BUFF_BITS [15:12]				AXI_RX_DESCR_RD_BUFF_BITS [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	RX_PBUF_DATA [23:20]				AXI_ACCESS_PIPELINE_BITS [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	EMAC_BUS_WIDTH [31:28]				TX_PBUF_DATA [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	AXI_RX_DESCR_WR_BUFF_BITS	R	R	1	Takes the value of the `gem_axi_rx_descr_wr_buff_bits DEFINE
4:7	AXI_TX_DESCR_WR_BUFF_BITS	R	R	1	Takes the value of the `gem_axi_tx_descr_wr_buff_bits DEFINE
8:11	AXI_RX_DESCR_RD_BUFF_BITS	R	R	1	Takes the value of the `gem_axi_rx_descr_rd_buff_bits DEFINE
12:15	AXI_TX_DESCR_RD_BUFF_BITS	R	R	1	Takes the value of the `gem_axi_tx_descr_rd_buff_bits DEFINE
16:19	AXI_ACCESS_PIPELINE_BITS	R	R	1	Takes the value of the `gem_axi_access_pipeline_bits DEFINE
20:23	RX_PBUF_DATA	R	R	4	Takes the value of the `gem_rx_pbuf_data DEFINE. 1 - The RX DPRAM has a datawidth of 32bits. 2 - The RX DPRAM has a datawidth of 64bits. 4 - RX The DPRAM has a datawidth of 128bits
24:27	TX_PBUF_DATA	R	R	4	Takes the value of the `gem_tx_pbuf_data DEFINE. 1 - The TX DPRAM has a datawidth of 32bits. 2 - The TX DPRAM has a datawidth of 64bits. 4 - The TX DPRAM has a datawidth of 128bits
28:31	EMAC_BUS_WIDTH	R	R	AXI_MASTER_PRESENT+1	Takes the value of the `gem_emac_bus_width DEFINE. 1 - The MAC has a datawidth of 32bits. 2 - The MAC has a datawidth of 64bits. 4 - The MAC has a datawidth of 128bits

11.1.146 ETH_SPEC_ADD5_BOTTOM

Description: Specific address registers 5 ~ 36 doesn't present. Access to the register returns AHB error.
Address: 0x40481300
Offset: 0x1300
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Write ignore, read 0

11.1.147 ETH_SPEC_ADD5_TOP

Description: Specific address registers 5 ~ 36 doesn't present. Access to the register returns AHB error.
Address: 0x40481304
Offset: 0x1304
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Write ignore, read 0

11.1.148 ETH_SPEC_ADD36_BOTTOM

Description: Not presents.
Address: 0x404813F8
Offset: 0x13F8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Write ignore, read 0

11.1.149 ETH_SPEC_ADD36_TOP

Description: Not presents.
Address: 0x404813FC
Offset: 0x13FC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESERVED_31_0	R	R	0	Write ignore, read 0

11.1.150 ETH_INT_Q1_STATUS

Description: Priority queue Interrupt Status Register
Address: 0x40481400
Offset: 0x1400
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT_COMPLETE [7:7]	AMBA_ERROR [6:6]	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION [5:5]	None [4:3]		RX_USED_BIT_READ [2:2]	RECEIVE_COMPLETE [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				RESP_NOT_OK [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	RECEIVE_COMPLETE	R	R	0	Receive complete
2	RX_USED_BIT_READ	R	R	0	RX used bit read
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION	R	R	0	Retry limit exceeded or late collision
6	AMBA_ERROR	R	R	0	Transmit frame corruption due to AMBA (AXI/AHB) error set if an error occurs whilst midway through reading transmit frame from the external memory, including HRESP (AHB), RRESP and BRESP errors (AXI) and buffers exhausted mid frame
7	TRANSMIT_COMPLETE	R	R	0	Transmit complete
11	RESP_NOT_OK	R	R	0	bresp not OK

11.1.151 ETH_INT_Q2_STATUS

Description: Priority queue Interrupt Status Register
Address: 0x40481404
Offset: 0x1404
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT_COMPLETE [7:7]	AMBA_ERROR [6:6]	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION [5:5]	None [4:3]		RX_USED_BIT_READ [2:2]	RECEIVE_COMPLETE [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				RESP_NOT_OK [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	RECEIVE_COMPLETE	R	R	0	Receive complete
2	RX_USED_BIT_READ	R	R	0	RX used bit read
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION	R	R	0	Retry limit exceeded or late collision
6	AMBA_ERROR	R	R	0	Transmit frame corruption due to AMBA (AXI/AHB) error set if an error occurs whilst midway through reading transmit frame from the external memory, including HRESP(AHB), RRESP and BRESP errors (AXI) and buffers exhausted mid frame
7	TRANSMIT_COMPLETE	R	R	0	Transmit complete
11	RESP_NOT_OK	R	R	0	bresp not OK

11.1.152 ETH_INT_Q3_STATUS

Description: int_q3_status to int_q15_status doesn't present. Access to the register returns AHB error.
Address: 0x40481408
Offset: 0x1408
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.153 ETH_INT_Q15_STATUS

Description: Not presents.
Address: 0x40481438
Offset: 0x1438
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.154 ETH_TRANSMIT_Q1_PTR

Description: This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.

Address: 0x40481440
Offset: 0x1440
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_TX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_TX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_TX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_TX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_TX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while transmit is not enabled.

Bits	Name	SW	HW	Default or Enum	Description
2:31	DMA_TX_Q_PTR	RW	RW	0	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AHB/AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit or 128bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AHB/AXI access. For 32bit datapaths, the descriptors should be aligned at 32-bit boundaries and the descriptors are read from memory using two individual 32-bit non sequential accesses.

11.1.155 ETH_TRANSMIT_Q2_PTR

Description: This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.

Address: 0x40481444
Offset: 0x1444
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_TX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_TX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_TX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_TX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_TX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while transmit is not enabled.

Bits	Name	SW	HW	Default or Enum	Description
2:31	DMA_TX_Q_PTR	RW	RW	0	This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AHB/AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit or 128bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AHB/AXI access. For 32bit datapaths, the descriptors should be aligned at 32-bit boundaries and the descriptors are read from memory using two individual 32-bit non sequential accesses

11.1.156 ETH_TRANSMIT_Q3_PTR

Description: transmit_q3_ptr to transmit_q15_ptr doesn't present. Access to the register returns AHB error.
Address: 0x40481448
Offset: 0x1448
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while transmit is not enabled.

11.1.157 ETH_TRANSMIT_Q15_PTR

Description: Not presents.
Address: 0x40481478
Offset: 0x1478
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.158 ETH_RECEIVE_Q1_PTR

Description: This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.

Address: 0x40481480
Offset: 0x1480
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_RX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_RX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_RX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_RX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_RX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while receive is not enabled.
2:31	DMA_RX_Q_PTR	RW	RW	0	Receive buffer queue base address - written with the address of the start of the receive queue.

11.1.159 ETH_RECEIVE_Q2_PTR

Description: This register holds the start address of the transmit buffer queue (transmit buffers descriptor list). The transmit buffer queue base address register must be initialized before transmit is started through bit 9 of the network control register. Once transmission has started, any write to the transmit buffer queue base address register is illegal and therefore ignored. Note that due to clock boundary synchronization, it takes a maximum of four pclk cycles from the writing of the transmit start bit before the transmitter is active. Writing to the transmit buffer queue base address register during this time may produce unpredictable results. Reading this register returns the location of the descriptor currently being accessed. Because the DMA can store data for multiple frames at once, this may not necessarily be pointing to the current frame being transmitted. In terms of AMBA AXI operation, the transmit descriptors are written to memory using a single 32bit AHB access. When the datapath is configured as 64bit, the transmit descriptors should be aligned at 64-bit boundaries and each pair of 32-bit descriptors is read from memory using a single AXI access.

Address: 0x40481484
Offset: 0x1484
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:1]	DMA_RX_DIS_Q [0:0]

Bits	15	14	13	12	11	10	9	8
Name	DMA_RX_Q_PTR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DMA_RX_Q_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DMA_RX_Q_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_RX_DIS_Q	RW	RW	0	Disable queue if set to 1. This can be used to reduce the number of active queues and should only be changed while receive is not enabled.
2:31	DMA_RX_Q_PTR	RW	RW	0	Receive buffer queue base address - written with the address of the start of the receive queue.

11.1.160 ETH_RECEIVE_Q3_PTR

Description: Not presents. Start address register doesn't present for queue3 ~ queue7.
Address: 0x40481488
Offset: 0x1488
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.161 ETH_RECEIVE_Q7_PTR

Description: Not presents.
Address: 0x40481498
Offset: 0x1498
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.162 ETH_DMA_RXBUF_SIZE_Q1

Description: Receive Buffer queue 1 Size
Address: 0x404814A0
Offset: 0x14A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x18

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_RX_Q_BUF_SIZE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DMA_RX_Q_BUF_SIZE	RW	RW	24	DMA receive buffer size in system memory. The value defined by these bits determines the size of buffer to use in main system memory when writing received data. The value is defined in multiples of 64 bytes. 0x01 corresponds to buffers of 64 bytes. 0x02 corresponds to 128 bytes etc. For example: 0x02: 128 byte 0x18: 1536 byte (1*max length frame/buffer) 0xA0: 10240 byte (1*10K jumbo frame/buffer) Note that this value should never be written as zero. Note. The reset value of this field is equal to the gem_rx_buffer_length_def define, which is user configurable.

11.1.163 ETH_DMA_RXBUF_SIZE_Q2

Description: Receive Buffer queue 2 Size
Address: 0x404814A4
Offset: 0x14A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x18

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DMA_RX_Q_BUF_SIZE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DMA_RX_Q_BUF_SIZE	RW	RW	24	DMA receive buffer size in system memory. The value defined by these bits determines the size of buffer to use in main system memory when writing received data. The value is defined in multiples of 64 bytes. 0x01 corresponds to buffers of 64 bytes. 0x02 corresponds to 128 bytes etc. For example: 0x02: 128 byte 0x18: 1536 byte (1*max length frame/buffer) 0xA0: 10240 byte (1*10K jumbo frame/buffer) Note that this value should never be written as zero. Note. The reset value of this field is equal to the gem_rx_buffer_length_def define, which is user configurable.

11.1.164 ETH_DMA_RXBUF_SIZE_Q3

Description: dma_rxbuf_size_q3 to dma_rxbuf_size_q7 doesn't present.
Address: 0x404814A8
Offset: 0x14A8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	DMA receive buffer size in system memory. The value defined by these bits determines the size of buffer to use in main system memory when writing received data. The value is defined in multiples of 64 bytes. 0x01 corresponds to buffers of 64 bytes. 0x02 corresponds to 128 bytes etc. For example: 0x02: 128 byte 0x18: 1536 byte (1*max length frame/buffer) 0xA0: 10240 byte (1*10K jumbo frame/buffer) Note that this value should never be written as zero. Note. The reset value of this field is equal to the gem_rx_buffer_length_def define, which is user configurable.

11.1.165 ETH_DMA_RXBUF_SIZE_Q7

Description: Not presents.
Address: 0x404814B8
Offset: 0x14B8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.166 ETH_CBS_CONTROL

Description: The IdleSlope value is defined as the rate of change of credit when a packet is waiting to be sent. This must not exceed the portTransmitRate which is dependent on the speed of operation, eg, portTransmitRate. 1Gb/s = 32'h07735940 (125 Mbytes/s), 100Mb/sec = 32'h017D7840 (25 Mnibbles/s), 10Mb/sec = 32'h002625A0 (2.5 Mnibbles/s). If 50 percent of bandwidth was to be allocated to a particular queue in 1Gb/sec mode then the IdleSlope value for that queue would be calculated as 32'h07735940/2. Note that Credit-Based Shaping should be disabled prior to updating the IdleSlope values. As another example, for a 1722 audio packet with a payload of 6 samples per channel, the packet size would be 7 (preamble) + 1 (SFD) + 50 (packet header) + 6x4x2(payload) + 4 (CRC) = 110 bytes. For a rate of 8000 packets per second, the desired rate would 110 x 8000 bytes per second, so the programmed idleSlope value would be 880000 for a 1Gb/s connection, or 1760000 for a 100Mb/s or 10Mbps connection. See Figure 6.3 in the IEEE 1722 standard. In practice, the actual transmission rate will be vary slightly from that calculated. In this case, the idleSlope value should be recalibrated based on the variance between the measured and expected rate, and in this case very accurate transmission rates can be achieved.

Address: 0x404814BC
Offset: 0x14BC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						CBS_ENABLE_QUEUE_B [1:1]	CBS_ENABLE_QUEUE_A [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CBS_ENABLE_QUEUE_A	RW	RW	0	Enable Credit-Based Shaping on the highest priority queue (queue A). Write 1 to enable
1	CBS_ENABLE_QUEUE_B	RW	RW	0	Enable Credit-Based shaping on the 2nd highest priority queue (queue B). Write 1 to enable

11.1.167 ETH_CBS_IDLESCOPE_Q_A

Description: queue A is the highest priority queue. This would be queue 8 in an 8 queue configuration.
Address: 0x404814C0
Offset: 0x14C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IDLESLOPE_A [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	IDLESLOPE_A [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	IDLESLOPE_A [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	IDLESLOPE_A [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	IDLESLOPE_A	RW	RW	0	IdleSlope value for queue A in bytes/sec for gigabit operation and nibbles/sec for 10/100 operation

11.1.168 ETH_CBS_IDLESCOPE_Q_B

Description: queue B is the 2nd highest priority queue. This would be queue 7 in an 8 queue configuration.
Address: 0x404814C4
Offset: 0x14C4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IDLESLOPE_B [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	IDLESLOPE_B [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	IDLESLOPE_B [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	IDLESLOPE_B [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	IDLESLOPE_B	RW	RW	0	IdleSlope value for queue B in bytes/sec for gigabit operation and nibbles/sec for 10/100 operation

11.1.169 ETH_UPPER_TX_Q_BASE_ADDR

Description: Upper 32 bits of transmit buffer descriptor queue base address.
Address: 0x404814C8
Offset: 0x14C8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UPPER_TX_Q_BASE_ADDR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	UPPER_TX_Q_BASE_ADDR [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	UPPER_TX_Q_BASE_ADDR [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	UPPER_TX_Q_BASE_ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	UPPER_TX_Q_BASE_ADDR	RW	RW	0	Upper 32 bits of transmit buffer descriptor queue base address. Used when 64 bit addressing is enabled. (In releases earlier to 1p06f2 this register also affected the receive descriptor queue.)

11.1.170 ETH_TX_BD_CONTROL

Description: TX BD control register
Address: 0x404814CC
Offset: 0x14CC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		TX_BD_TS_MODE [5:4]		None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:5	TX_BD_TS_MODE	RW	RW	0	TX Descriptor Timestamp Insertion mode, 00: TS insertion disable, 01: TS inserted for PTP Event Frames only, 10: TS inserted for All PTP Frames only, 11: TS insertion for All Frames

11.1.171 ETH_RX_BD_CONTROL

Description: RX BD control register
Address: 0x404814D0
Offset: 0x14D0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RX_BD_TS_MODE [5:4]		None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4:5	RX_BD_TS_MODE	RW	RW	0	RX Descriptor Timestamp Insertion mode, 00: TS insertion disable, 01: TS inserted for PTP Event Frames only, 10: TS inserted for All PTP Frames only, 11: TS insertion for All Frames

11.1.172 ETH_UPPER_RX_Q_BASE_ADDR

Description: Upper 32 bits of receive buffer descriptor queue base address.
Address: 0x404814D4
Offset: 0x14D4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UPPER_RX_Q_BASE_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	UPPER_RX_Q_BASE_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	UPPER_RX_Q_BASE_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	UPPER_RX_Q_BASE_ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	UPPER_RX_Q_BASE_ADDR	RW	RW	0	Upper 32 bits of receive buffer descriptor queue base address. Used when 64 bit addressing is enabled.

11.1.173 ETH_HIDDEN_REG0

Description: Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_10m 12'h4e0 // 10M Port TX Rate *** HIDDEN Register ***. Default value of cbs related hidden registers (0x14E0~0x14E8) are depicted in cbs_control register.

Address: 0x404814E0

Offset: 0x14E0

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x2625A0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	HIDDEN0_FIELD [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	HIDDEN0_FIELD [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	HIDDEN0_FIELD [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	HIDDEN0_FIELD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	HIDDEN0_FIELD	RW	RW	2500000	default value is defined per description of register cbs_control.

11.1.174 ETH_HIDDEN_REG1

Description: Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_100m 12'h4e4 // 100M Port TX Rate *** HIDDEN Register ***
Address: 0x404814E4
Offset: 0x14E4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x17D7840

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	HIDDEN1_FIELD [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	HIDDEN1_FIELD [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	HIDDEN1_FIELD [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	HIDDEN1_FIELD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	HIDDEN1_FIELD	RW	RW	25000000	default value is defined per description of register cbs_control.

11.1.175 ETH_HIDDEN_REG2

Description: Hidden registers defined in edma_defs.v ``define gem_cbs_port_tx_rate_1g 12'h4e8 // 1G Port TX Rate *** HIDDEN Register ***
Address: 0x404814E8
Offset: 0x14E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x7735940

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	HIDDEN2_FIELD [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	HIDDEN2_FIELD [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	HIDDEN2_FIELD [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	HIDDEN2_FIELD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	HIDDEN2_FIELD	RW	RW	125000000	default value is defined per description of register cbs_control.

11.1.176 ETH_HIDDEN_REG3

Description: Hidden registers defined in edma_defs.v ``define gem_wd_counter 12'h4ec // *** HIDDEN Register ***.
Address: 0x404814EC
Offset: 0x14EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x7

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				HIDDEN3_FIELD [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	HIDDEN3_FIELD	RW	RW	7	default value is defined per description of register cbs_control.

11.1.177 ETH_SCREENING_TYPE_1_REGISTER_0

Description: Screening type 1 registers are used to allocate up to 16 priority queues to received frames based on certain IP or UDP fields of incoming frames. Firstly, when DS/TC match enable is set (bit 28), the DS (Differentiated Services) field of the received IPv4 header or TCfield (traffic class) of IPv6 headers are matched against bits 11 to 4. Secondly, when UDP port match enable is set (bit 29), the UDP Destination Port of the received UDP frame is matched against bits 27 to 12. Both UDP and DS/TC matching can be enabled simultaneously or individually. If a match is successful, then the queue value programmed in bits 2 to 0 is allocated to the frame. The required number of Type 1 screening registers is configured in the gem defines file. Up to 16 type 1 screening registers have been allocated APB address space between 0x500 and 0x53C.

Address: 0x40481500
Offset: 0x1500
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			
Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.178 ETH_SCREENING_TYPE_1_REGISTER_1

Description: screening type 1 register 1, same as screening_type_1_register_0
Address: 0x40481504
Offset: 0x1504
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.179 ETH_SCREENING_TYPE_1_REGISTER_2

Description: screening type 1 register 2, same as screening_type_1_register_0
Address: 0x40481508
Offset: 0x1508
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.180 ETH_SCREENING_TYPE_1_REGISTER_3

Description: screening type 1 register 3, same as screening_type_1_register_0
Address: 0x4048150C
Offset: 0x150C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.181 ETH_SCREENING_TYPE_1_REGISTER_4

Description: screening type 1 register 4, same as screening_type_1_register_0
Address: 0x40481510
Offset: 0x1510
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.182 ETH_SCREENING_TYPE_1_REGISTER_5

Description: screening type 1 register 5, same as screening_type_1_register_0
Address: 0x40481514
Offset: 0x1514
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.183 ETH_SCREENING_TYPE_1_REGISTER_6

Description: screening type 1 register 6, same as screening_type_1_register_0
Address: 0x40481518
Offset: 0x1518
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.184 ETH_SCREENING_TYPE_1_REGISTER_7

Description: screening type 1 register 7, same as screening_type_1_register_0
Address: 0x4048151C
Offset: 0x151C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.185 ETH_SCREENING_TYPE_1_REGISTER_8

Description: screening type 1 register 8, same as screening_type_1_register_0
Address: 0x40481520
Offset: 0x1520
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.186 ETH_SCREENING_TYPE_1_REGISTER_9

Description: screening type 1 register 9, same as screening_type_1_register_0
Address: 0x40481524
Offset: 0x1524
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.187 ETH_SCREENING_TYPE_1_REGISTER_10

Description: screening type 1 register 10, same as screening_type_1_register_0
Address: 0x40481528
Offset: 0x1528
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.188 ETH_SCREENING_TYPE_1_REGISTER_11

Description: screening type 1 register 11, same as screening_type_1_register_0
Address: 0x4048152C
Offset: 0x152C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.189 ETH_SCREENING_TYPE_1_REGISTER_12

Description: screening type 1 register 12, same as screening_type_1_register_0
Address: 0x40481530
Offset: 0x1530
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.190 ETH_SCREENING_TYPE_1_REGISTER_13

Description: screening type 1 register 13, same as screening_type_1_register_0
Address: 0x40481534
Offset: 0x1534
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.191 ETH_SCREENING_TYPE_1_REGISTER_14

Description: screening type 1 register 14, same as screening_type_1_register_0
Address: 0x40481538
Offset: 0x1538
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.192 ETH_SCREENING_TYPE_1_REGISTER_15

Description: screening type 1 register 15, same as screening_type_1_register_0
Address: 0x4048153C
Offset: 0x153C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name					DSTC_MATCH [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	UDP_PORT_MATCH [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		UDP_PORT_MATCH_ENABLE [29:29]	DSTC_ENABLE [28:28]	UDP_PORT_MATCH [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	Queue Number (0 to 15)
4:11	DSTC_MATCH	RW	RW	0	DS/TC Match
12:27	UDP_PORT_MATCH	RW	RW	0	UDP Port Match
28	DSTC_ENABLE	RW	RW	0	DS/TC Enable
29	UDP_PORT_MATCH_ENABLE	RW	RW	0	UDP port match enable

11.1.193 ETH_SCREENING_TYPE_2_REGISTER_0

Description:	Screener Type 2 match registers operate independently of screener type 1 registers and offer additional match capabilities, extending the capabilities into vendor specific protocols.
Address:	0x40481540
Offset:	0x1540
Retention:	Not Retained
IsDeepSleep:	No
Comment:	'Screener Type 2 match registers allow a screen to be configured that is the combination of all or any of the following comparisons: 1) An enabled VLAN Priority. A VLAN Priority match will be performed if the VLAN priority enable is set. The extracted priority field in the VLAN header is compared against 3 bits within the screener type 2 register itself. 2) An enabled EtherType. 3) An enabled Field Compare A. 4) An enabled Field Compare B. 5) An enabled Field Compare C. The required number of Type 2 screening registers is configured in the gem defines file. Up to 16 type 2 screening registers have been allocated APB address space between 0x540 and 0x57C. The bit mappings for these registers is as follows:'
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'

Bits	Name	SW	HW	Default or Enum	Description
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.194 ETH_SCREENING_TYPE_2_REGISTER_1

Description: screening type 2 register 1, same as screening_type_2_register_0
Address: 0x40481544
Offset: 0x1544
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.195 ETH_SCREENING_TYPE_2_REGISTER_2

Description: screening type 2 register 2, same as screening_type_2_register_0
Address: 0x40481548
Offset: 0x1548
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.196 ETH_SCREENING_TYPE_2_REGISTER_3

Description: screening type 2 register 3, same as screening_type_2_register_0
Address: 0x4048154C
Offset: 0x154C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.197 ETH_SCREENING_TYPE_2_REGISTER_4

Description: screening type 2 register 4, same as screening_type_2_register_0
Address: 0x40481550
Offset: 0x1550
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.198 ETH_SCREENING_TYPE_2_REGISTER_5

Description: screening type 2 register 5, same as screening_type_2_register_0
Address: 0x40481554
Offset: 0x1554
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.199 ETH_SCREENING_TYPE_2_REGISTER_6

Description: screening type 2 register 6, same as screening_type_2_register_0
Address: 0x40481558
Offset: 0x1558
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.200 ETH_SCREENING_TYPE_2_REGISTER_7

Description: screening type 2 register 7, same as screening_type_2_register_0
Address: 0x4048155C
Offset: 0x155C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.201 ETH_SCREENING_TYPE_2_REGISTER_8

Description: screening type 2 register 8, same as screening_type_2_register_0
Address: 0x40481560
Offset: 0x1560
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.202 ETH_SCREENING_TYPE_2_REGISTER_9

Description: screening type 2 register 9, same as screening_type_2_register_0
Address: 0x40481564
Offset: 0x1564
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.203 ETH_SCREENING_TYPE_2_REGISTER_10

Description: screening type 2 register 10, same as screening_type_2_register_0
Address: 0x40481568
Offset: 0x1568
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.204 ETH_SCREENING_TYPE_2_REGISTER_11

Description: screening type 2 register 11, same as screening_type_2_register_0
Address: 0x4048156C
Offset: 0x156C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.205 ETH_SCREENING_TYPE_2_REGISTER_12

Description: screening type 2 register 12, same as screening_type_2_register_0
Address: 0x40481570
Offset: 0x1570
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.206 ETH_SCREENING_TYPE_2_REGISTER_13

Description: screening type 2 register 13, same as screening_type_2_register_0
Address: 0x40481574
Offset: 0x1574
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.207 ETH_SCREENING_TYPE_2_REGISTER_14

Description: screening type 2 register 14, same as screening_type_2_register_0
Address: 0x40481578
Offset: 0x1578
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.208 ETH_SCREENING_TYPE_2_REGISTER_15

Description: screening type 2 register 15, same as screening_type_2_register_0
Address: 0x4048157C
Offset: 0x157C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7 [7:7]	VLAN_PRIORITY [6:4]			QUEUE_NUMBER [3:0]			

Bits	15	14	13	12	11	10	9	8
Name				ETHERTYPE_ENABLE [12:12]	INDEX [11:9]			VLAN_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_B [23:19]					COMPARE_A_ENABLE [18:18]	COMPARE_A [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31 [31:31]	COMPARE_C_ENABLE [30:30]	COMPARE_C [29:25]					COMPARE_B_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	QUEUE_NUMBER	RW	RW	0	'Queue Number (0 to 15)'
4:6	VLAN_PRIORITY	RW	RW	0	'VLAN Priority'
7	RESERVED_7	RW	RW	0	'Reserved and implemented as RW'
8	VLAN_ENABLE	RW	RW	0	'VLAN Enable'
9:11	INDEX	RW	RW	0	'Index to screener type 2 EtherType register'
12	ETHERTYPE_ENABLE	RW	RW	0	'EtherType Enable'
13:17	COMPARE_A	RW	RW	0	'Compare A - Index to screener type 2 Compare register'
18	COMPARE_A_ENABLE	RW	RW	0	'Compare A Enable'
19:23	COMPARE_B	RW	RW	0	'Compare B - Index to screener type 2 Compare register'
24	COMPARE_B_ENABLE	RW	RW	0	'Compare B Enable'
25:29	COMPARE_C	RW	RW	0	'Compare C - Index to screener type 2 Compare register'
30	COMPARE_C_ENABLE	RW	RW	0	'Compare C Enable'
31	RESERVED_31	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.209 ETH_TX_SCHED_CTRL

Description: This register controls the transmit scheduling algorithm the user can select for each active transmit queue. By default all queues are initialized to fixed priority, with the top indexed queue having overall priority

Address: 0x40481580

Offset: 0x1580

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TX_SCHED_Q3 [7:6]		TX_SCHED_Q2 [5:4]		TX_SCHED_Q1 [3:2]		TX_SCHED_Q0 [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_8 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_8 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_8 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	TX_SCHED_Q0	RW	RW	0	'Queue 0 selection. 00 : Fixed Priority 01 : CBS Enabled only valid for top two enabled queues and if CBS capability selected. 10 : DWRR Enabled 11 : ETS Enabled'
2:3	TX_SCHED_Q1	RW	RW	0	'Queue 1 selection. 00 : Fixed Priority 01 : CBS Enabled only valid for top two enabled queues and if CBS capability selected. 10 : DWRR Enabled 11 : ETS Enabled'
4:5	TX_SCHED_Q2	RW	RW	0	'Queue 2 selection. 00 : Fixed Priority 01 : CBS Enabled only valid for top two enabled queues and if CBS capability selected. 10 : DWRR Enabled 11 : ETS Enabled'
6:7	TX_SCHED_Q3	R	R	0	Write ignore, read 0
8:31	REMOVED_31_8	R	R	0	Write ignore, read 0

11.1.210 ETH_BW_RATE_LIMIT_Q0TO3

Description: This register holds the DWRR weighting value or the ETS bandwidth percentage value used by the transmit scheduler for queues 0 to 3.

Address: 0x40481590

Offset: 0x1590

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DWRR_ETS_WEIGHT_Q0 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DWRR_ETS_WEIGHT_Q1 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DWRR_ETS_WEIGHT_Q2 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DWRR_ETS_WEIGHT_Q3 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DWRR_ETS_WEIGHT_Q0	RW	RW	0	'DWRR Weighting / ETS Bandwidth Allocation for queue 0'
8:15	DWRR_ETS_WEIGHT_Q1	RW	RW	0	'DWRR Weighting / ETS Bandwidth Allocation for queue 1'
16:23	DWRR_ETS_WEIGHT_Q2	RW	RW	0	'DWRR Weighting / ETS Bandwidth Allocation for queue 2'
24:31	DWRR_ETS_WEIGHT_Q3	R	R	0	Write ignore, read 0

11.1.211 ETH_BW_RATE_LIMIT_Q4TO7

Description: Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
Address: 0x40481594
Offset: 0x1594
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	RW	RW	0	'DWRR Weighting / ETS Bandwidth Allocation for queue 0'

11.1.212 ETH_BW_RATE_LIMIT_Q8TO11

Description: Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
Address: 0x40481598
Offset: 0x1598
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.213 ETH_BW_RATE_LIMIT_Q12TO15

Description: Not presents. MXETH has only 3 queues. Access to the register returns AHB error.
Address: 0x4048159C
Offset: 0x159C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.214 ETH_TX_Q_SEG_ALLOC_Q0T07

Description: This register allows the user to distribute the Transmit SRAM used by the DMA across the priority queues, for queues 0 to 7. The SRAM itself is split into a number of evenly sized segments (this is defined in the verilog configuration defs file - for the configuration used to generate this register description, the total number of segments was set to '16'). Those segments can then be freely distributed across the active queues, in powers of 2. I.e. a value of 0 would mean 1 segment has been allocated to the queue. A value of 1 would mean 2 segments, a value of 2 means 4 segments and so on. The reset values of these registers are defined in the configuration defs file.

Address: 0x404815A0
Offset: 0x15A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESERVED_7_7 [7:7]	SEGMENT_ALLOC_Q1 [6:4]			RESERVED_3_3 [3:3]	SEGMENT_ALLOC_Q0 [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	RESERVED_15_15 [15:15]	REMOVED_14_12 [14:12]			RESERVED_11_11 [11:11]	SEGMENT_ALLOC_Q2 [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_23 [23:23]	REMOVED_22_20 [22:20]			RESERVED_19_19 [19:19]	REMOVED_18_16 [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_31 [31:31]	REMOVED_30_28 [30:28]			RESERVED_27_27 [27:27]	REMOVED_26_24 [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	SEGMENT_ALLOC_Q0	RW	RW	1	Number of segments allocated to q0. This should be entered as a log 2, for example entering a value of 2 would grant 4 segments. A maximum of 32 segments can be granted. The default value is determined by 'gem_tx_pbuf_num_segments_q0'
3	RESERVED_3_3	R	R	0	Reserved, read as 0, ignored on write.
4:6	SEGMENT_ALLOC_Q1	RW	RW	0	Number of segments allocated to q1. This should be entered as a log 2, for example entering a value of 2 would grant 4 segments. A maximum of 32 segments can be granted
7	RESERVED_7_7	R	R	0	Reserved, read as 0, ignored on write.
8:10	SEGMENT_ALLOC_Q2	RW	RW	0	Number of segments allocated to q2. This should be entered as a log 2, for example entering a value of 2 would grant 4 segments. A maximum of 32 segments can be granted
11	RESERVED_11_11	R	R	0	Write ignore, read 0
12:14	REMOVED_14_12	R	R	0	Write ignore, read 0
15	RESERVED_15_15	R	R	0	Write ignore, read 0
16:18	REMOVED_18_16	R	R	0	Write ignore, read 0
19	RESERVED_19_19	R	R	0	Write ignore, read 0

Bits	Name	SW	HW	Default or Enum	Description
20:22	REMOVED_22_20	R	R	0	Write ignore, read 0
23	RESERVED_23	R	R	0	Write ignore, read 0
24:26	REMOVED_26_24	R	R	0	Write ignore, read 0
27	RESERVED_27_27	R	R	0	Write ignore, read 0
28:30	REMOVED_30_28	R	R	0	Write ignore, read 0
31	RESERVED_31_31	R	R	0	Write ignore, read 0

11.1.215 ETH_TX_Q_SEG_ALLOC_Q8TO15

Description: Not presents. Access to the register returns AHB error.
Address: 0x404815A4
Offset: 0x15A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.216 ETH_RECEIVE_Q8_PTR

Description: receive_q8_ptr to receive_q15_ptr doesn't present. Access to the register returns AHB error.
Address: 0x404815C0
Offset: 0x15C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.217 ETH_RECEIVE_Q15_PTR

Description: Not presents.
Address: 0x404815DC
Offset: 0x15DC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.218 ETH_DMA_RXBUF_SIZE_Q8

Description: dma_rxbuf_size_q8 to dma_rxbuf_size_q15 doesn't present. Access to the register returns AHB error.
Address: 0x404815E0
Offset: 0x15E0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.219 ETH_DMA_RXBUF_SIZE_Q15

Description: Not presents.
Address: 0x404815FC
Offset: 0x15FC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.220 ETH_INT_Q1_ENABLE

Description: At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.

Address: 0x40481600

Offset: 0x1600

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ENABLE_TRANSMIT_COMPLETE_INTERRUPT [7:7]	ENABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT [6:6]	ENABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT [5:5]	None [4:3]		ENABLE_RX_USED_BIT_READ_INTERRUPT [2:2]	ENABLE_RECEIVE_COMPLETE_INTERRUPT [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				ENABLE_RESP_NOT_OK_INTERRUPT [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	ENABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	Enable Receive complete interrupt
2	ENABLE_RX_USED_BIT_READ_INTERRUPT	W	W	0	Enable RX used bit read interrupt
5	ENABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	Enable Retry limit exceeded or late collision interrupt
6	ENABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	Enable Transmit frame corruption due to AMBA (AXI/AHB) error interrupt
7	ENABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	Enable Transmit complete interrupt
11	ENABLE_RESP_NOT_OK_INTERRUPT	W	W	0	Enable bresp not OK interrupt

11.1.221 ETH_INT_Q2_ENABLE

Description: At reset all interrupts are disabled. Writing a one to the relevant bit location enables the required interrupt. This register is write only and when read will return zero.

Address: 0x40481604

Offset: 0x1604

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ENABLE_TRANSMIT_COMPLETE_INTERRUPT [7:7]	ENABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT [6:6]	ENABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT [5:5]	None [4:3]		ENABLE_RX_USED_BIT_READ_INTERRUPT [2:2]	ENABLE_RECEIVE_COMPLETE_INTERRUPT [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				ENABLE_RESP_NOT_OK_INTERRUPT [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	ENABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	Enable Receive complete interrupt
2	ENABLE_RX_USED_BIT_READ_INTERRUPT	W	W	0	Enable RX used bit read interrupt
5	ENABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	Enable Retry limit exceeded or late collision interrupt
6	ENABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	Enable Transmit frame corruption due to AMBA (AXI/AHB) error interrupt
7	ENABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	Enable Transmit complete interrupt
11	ENABLE_RESP_NOT_OK_INTERRUPT	W	W	0	Enable bresp not OK interrupt

11.1.222 ETH_INT_Q3_ENABLE

Description: int_q3_enable to int_q7_enable doesn't present. Access to the register returns AHB error.
Address: 0x40481608
Offset: 0x1608
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.223 ETH_INT_Q7_ENABLE

Description: Not presents.
Address: 0x40481618
Offset: 0x1618
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.224 ETH_INT_Q1_DISABLE

Description: Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.

Address: 0x40481620

Offset: 0x1620

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DISABLE_TRANSMIT_COMPLETE_INTERRUPT [7:7]	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT [6:6]	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT [5:5]	None [4:3]		DISABLE_RX_USED_BIT_READ_INTERRUPT [2:2]	DISABLE_RECEIVE_COMPLETE_INTERRUPT [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				DISABLE_RESP_NOT_OK_INTERRUPT [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	DISABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	Disable Receive complete interrupt
2	DISABLE_RX_USED_BIT_READ_INTERRUPT	W	W	0	Disable RX used bit read interrupt
5	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	Disable Retry limit exceeded or late collision interrupt
6	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	Disable Transmit frame corruption due to AMBA (AXI/AHB) error interrupt
7	DISABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	Disable Transmit complete interrupt
11	DISABLE_RESP_NOT_OK_INTERRUPT	W	W	0	Disable bresp not OK interrupt

11.1.225 ETH_INT_Q2_DISABLE

Description: Writing a 1 to the relevant bit location disables that particular interrupt. This register is write only and when read will return zero.

Address: 0x40481624

Offset: 0x1624

Retention: Not Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DISABLE_TRANSMIT_COMPLETE_INTERRUPT [7:7]	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT [6:6]	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT [5:5]	None [4:3]		DISABLE_RX_USED_BIT_READ_INTERRUPT [2:2]	DISABLE_RECEIVE_COMPLETE_INTERRUPT [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				DISABLE_RESP_NOT_OK_INTERRUPT [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	DISABLE_RECEIVE_COMPLETE_INTERRUPT	W	W	0	Disable Receive complete interrupt
2	DISABLE_RX_USED_BIT_READ_INTERRUPT	W	W	0	Disable RX used bit read interrupt
5	DISABLE_RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT	W	W	0	Disable Retry limit exceeded or late collision interrupt
6	DISABLE_TRANSMIT_FRAME_CORRUPTION_DUE_TO_AMBA_ERROR_INTERRUPT	W	W	0	Disable Transmit frame corruption due to AMBA (AXI/AHB) error interrupt
7	DISABLE_TRANSMIT_COMPLETE_INTERRUPT	W	W	0	Disable Transmit complete interrupt
11	DISABLE_RESP_NOT_OK_INTERRUPT	W	W	0	Disable bresp not OK interrupt

11.1.226 ETH_INT_Q3_DISABLE

Description: int_q3_disable to int_q7_disable doesn't present. Access to the register returns AHB error.
Address: 0x40481628
Offset: 0x1628
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.227 ETH_INT_Q7_DISABLE

Description: Not presents.
Address: 0x40481638
Offset: 0x1638
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.228 ETH_INT_Q1_MASK

Description: The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.

Address: 0x40481640
Offset: 0x1640
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x8E6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT COMPLETE _INTERRUPT _MASK [7:7]	AMBA ERROR _INTERRUPT _MASK [6:6]	RETRY LIMIT _EXCEED _D_OR _LATE COLLISION _INTERRUPT _MASK [5:5]	None [4:3]		RX_USED _INTERRUPT _MASK [2:2]	RECEIVE _COMPLETE _INTERRUPT _MASK [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				RESP_NOT OK _INTERRUPT _MASK [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	RECEIVE_COMPLETE_INTERRUPT_MASK	R	R	1	receive complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
2	RX_USED_INTERRUPT_MASK	R	R	1	A read of this register returns the value of the RX Used interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

Bits	Name	SW	HW	Default or Enum	Description
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT_MASK	R	R	1	retry limit exceeded or late collision interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
6	AMBA_ERROR_INTERRUPT_MASK	R	R	1	A read of this register returns the value of the AMBA (AXI/AHB) error interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
7	TRANSMIT_COMPLETE_INTERRUPT_MASK	R	R	1	transmit complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
11	RESP_NOT_OK_INTERRUPT_MASK	R	R	1	bresp not OK interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

11.1.229 ETH_INT_Q2_MASK

Description: The interrupt mask register is a read only register indicating which interrupts are masked. All bits are set at reset and can be reset individually by writing to the interrupt enable register or set individually by writing to the interrupt disable register. Having separate address locations for enable and disable saves the need for performing a read modify write when updating the interrupt mask register. For test purposes there is a write-only function to this register that allows the bits in the interrupt status register to be set or cleared, regardless of the state of the mask register.

Address: 0x40481644
Offset: 0x1644
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x8E6

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRANSMIT COMPLETE _INTERRUPT _MASK [7:7]	AMBA ERROR _INTERRUPT _MASK [6:6]	RETRY LIMIT _EXCEED _D_OR _LATE COLLISION _INTERRUPT _MASK [5:5]	None [4:3]		RX_USED _INTERRUPT _MASK [2:2]	RECEIVE _COMPLETE _INTERRUPT _MASK [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				RESP_NOT OK _INTERRUPT _MASK [11:11]	None [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	RECEIVE_COMPLETE_INTERRUPT_MASK	R	R	1	receive complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
2	RX_USED_INTERRUPT_MASK	R	R	1	A read of this register returns the value of the RX Used interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

Bits	Name	SW	HW	Default or Enum	Description
5	RETRY_LIMIT_EXCEEDED_OR_LATE_COLLISION_INTERRUPT_MASK	R	R	1	retry limit exceeded or late collision interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
6	AMBA_ERROR_INTERRUPT_MASK	R	R	1	A read of this register returns the value of the AMBA (AXI/AHB) error interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
7	TRANSMIT_COMPLETE_INTERRUPT_MASK	R	R	1	transmit complete interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.
11	RESP_NOT_OK_INTERRUPT_MASK	R	R	1	bresp not OK interrupt mask. 0: Interrupt is enabled. 1: Interrupt is disabled. A write to this register directly affects the state of the corresponding bit in the interrupt status register, causing an interrupt to be generated if a 1 is written.

11.1.230 ETH_INT_Q3_MASK

Description: int_q3_mask to int_q7_mask doesn't present. Access to the register returns AHB error.
Address: 0x40481648
Offset: 0x1648
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.231 ETH_INT_Q7_MASK

Description: Not presents.
Address: 0x40481658
Offset: 0x1658
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.232 ETH_INT_Q8_ENABLE

Description: int_q8_enable to int_q15_enable doesn't present. Access to the register returns AHB error.
Address: 0x40481660
Offset: 0x1660
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.233 ETH_INT_Q15_ENABLE

Description: Not presents.
Address: 0x4048167C
Offset: 0x167C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.234 ETH_INT_Q8_DISABLE

Description: int_q8_disable to int_q15_disable doesn't present. Access to the register returns AHB error.
Address: 0x40481680
Offset: 0x1680
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.235 ETH_INT_Q15_DISABLE

Description: Not presents.
Address: 0x4048169C
Offset: 0x169C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.236 ETH_INT_Q8_MASK

Description: int_q8_mask to int_q15_mask doesn't present. Access to the register returns AHB error.
Address: 0x404816A0
Offset: 0x16A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.237 ETH_INT_Q15_MASK

Description: Not presents.
Address: 0x404816BC
Offset: 0x16BC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REMOVED_31_0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	REMOVED_31_0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	REMOVED_31_0 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REMOVED_31_0 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	REMOVED_31_0	R	R	0	Write ignore, read 0

11.1.238 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_0

Description: Ethertype Register
Address: 0x404816E0
Offset: 0x16E0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.239 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_1

Description: Ethertype Register
Address: 0x404816E4
Offset: 0x16E4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.240 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_2

Description: Ethertype Register
Address: 0x404816E8
Offset: 0x16E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.241 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_3

Description: Ethertype Register
Address: 0x404816EC
Offset: 0x16EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.242 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_4

Description: Ethertype Register
Address: 0x404816F0
Offset: 0x16F0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.243 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_5

Description: Ethertype Register
Address: 0x404816F4
Offset: 0x16F4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.244 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_6

Description: Ethertype Register
Address: 0x404816F8
Offset: 0x16F8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.245 ETH_SCREENING_TYPE_2_ETHERTYPE_REG_7

Description: Ethertype Register
Address: 0x404816FC
Offset: 0x16FC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMPARE_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMPARE_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_16 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMPARE_VALUE	RW	RW	0	'EtherType compare value'
16:31	RESERVED_31_16	R	R	0	'Reserved, read as 0, ignored on write '

11.1.246 ETH_TYPE2_COMPARE_0_WORD_0

Description:	'Compare A, B and C fields of the screener type 2 match register are pointers to a pool of up to 32 compare registers. If enabled the compare is true if the data at the OFFSET into the frame, ANDed with the MASK Value if the mask is enabled, is equal to the COMPARE Value. Either a 16 bit comparison or a 32 bit comparison is done. This selection is made via the associated compare word1 register bit 9. If a 16 bit comparison is selected, then a 16 bit mask is also available to the user to select which bits should be compared. If the 32 bit compare option is selected, then no mask is available. The byte at the OFFSET number of bytes from the index start is compared thru bits 7 to 0 of the configured VALUE. The byte at the OFFSET number of bytes + 1 from the index start is compared thru bits 15 to 8 of the configured VALUE and so on. The OFFSET can be configured to be from 0 to 127 bytes from either the start of the frame, the byte following the therType field (last EtherType in the header if the frame is VLAN tagged), the byte following the IP header (IPv4 or IPv6) or from the byte following the start of the TCP/UDP header. The required number of Type 2 screening registers up to a maximum of 32 is configurable in the gem defines file and have been allocated APB address space between 0x700 and 0x7fc. Note. when using RX Partial Store and Forward mode and priority queues, the frame offset must be less than the Partial Store and Forward watermark. If the offset is higher than the watermark value it's not possible to identify the priority queue before the frame is sent to the AMBA interface, and an incorrect priority queue may be used. '
Address:	0x40481700
Offset:	0x1700
Retention:	Not Retained
IsDeepSleep:	No
Comment:	
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].

Bits	Name	SW	HW	Default or Enum	Description
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.247 ETH_TYPE2_COMPARE_0_WORD_1

Description: 'Type2 Compare Word 1'
Address: 0x40481704
Offset: 0x1704
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							
Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]
Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.248 ETH_TYPE2_COMPARE_1_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481708
Offset: 0x1708
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.249 ETH_TYPE2_COMPARE_1_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048170C
Offset: 0x170C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.250 ETH_TYPE2_COMPARE_2_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481710
Offset: 0x1710
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.251 ETH_TYPE2_COMPARE_2_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481714
Offset: 0x1714
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.252 ETH_TYPE2_COMPARE_3_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481718
Offset: 0x1718
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.253 ETH_TYPE2_COMPARE_3_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048171C
Offset: 0x171C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.254 ETH_TYPE2_COMPARE_4_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481720
Offset: 0x1720
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.255 ETH_TYPE2_COMPARE_4_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481724
Offset: 0x1724
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.256 ETH_TYPE2_COMPARE_5_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481728
Offset: 0x1728
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.257 ETH_TYPE2_COMPARE_5_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048172C
Offset: 0x172C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.258 ETH_TYPE2_COMPARE_6_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481730
Offset: 0x1730
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.259 ETH_TYPE2_COMPARE_6_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481734
Offset: 0x1734
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.260 ETH_TYPE2_COMPARE_7_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481738
Offset: 0x1738
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.261 ETH_TYPE2_COMPARE_7_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048173C
Offset: 0x173C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.262 ETH_TYPE2_COMPARE_8_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481740
Offset: 0x1740
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.263 ETH_TYPE2_COMPARE_8_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481744
Offset: 0x1744
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.264 ETH_TYPE2_COMPARE_9_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481748
Offset: 0x1748
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.265 ETH_TYPE2_COMPARE_9_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048174C
Offset: 0x174C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.266 ETH_TYPE2_COMPARE_10_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481750
Offset: 0x1750
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.267 ETH_TYPE2_COMPARE_10_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481754
Offset: 0x1754
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.268 ETH_TYPE2_COMPARE_11_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481758
Offset: 0x1758
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.269 ETH_TYPE2_COMPARE_11_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048175C
Offset: 0x175C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.270 ETH_TYPE2_COMPARE_12_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481760
Offset: 0x1760
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.271 ETH_TYPE2_COMPARE_12_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481764
Offset: 0x1764
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.272 ETH_TYPE2_COMPARE_13_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481768
Offset: 0x1768
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.273 ETH_TYPE2_COMPARE_13_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048176C
Offset: 0x176C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.274 ETH_TYPE2_COMPARE_14_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481770
Offset: 0x1770
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.275 ETH_TYPE2_COMPARE_14_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481774
Offset: 0x1774
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.276 ETH_TYPE2_COMPARE_15_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481778
Offset: 0x1778
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.277 ETH_TYPE2_COMPARE_15_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048177C
Offset: 0x177C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.278 ETH_TYPE2_COMPARE_16_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481780
Offset: 0x1780
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.279 ETH_TYPE2_COMPARE_16_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481784
Offset: 0x1784
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.280 ETH_TYPE2_COMPARE_17_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481788
Offset: 0x1788
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.281 ETH_TYPE2_COMPARE_17_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048178C
Offset: 0x178C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.282 ETH_TYPE2_COMPARE_18_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481790
Offset: 0x1790
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.283 ETH_TYPE2_COMPARE_18_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x40481794
Offset: 0x1794
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.284 ETH_TYPE2_COMPARE_19_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x40481798
Offset: 0x1798
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.285 ETH_TYPE2_COMPARE_19_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x4048179C
Offset: 0x179C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.286 ETH_TYPE2_COMPARE_20_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817A0
Offset: 0x17A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.287 ETH_TYPE2_COMPARE_20_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817A4
Offset: 0x17A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.288 ETH_TYPE2_COMPARE_21_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817A8
Offset: 0x17A8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.289 ETH_TYPE2_COMPARE_21_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817AC
Offset: 0x17AC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.290 ETH_TYPE2_COMPARE_22_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817B0
Offset: 0x17B0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.291 ETH_TYPE2_COMPARE_22_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817B4
Offset: 0x17B4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.292 ETH_TYPE2_COMPARE_23_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817B8
Offset: 0x17B8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.293 ETH_TYPE2_COMPARE_23_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817BC
Offset: 0x17BC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.294 ETH_TYPE2_COMPARE_24_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817C0
Offset: 0x17C0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.295 ETH_TYPE2_COMPARE_24_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817C4
Offset: 0x17C4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.296 ETH_TYPE2_COMPARE_25_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817C8
Offset: 0x17C8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.297 ETH_TYPE2_COMPARE_25_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817CC
Offset: 0x17CC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.298 ETH_TYPE2_COMPARE_26_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817D0
Offset: 0x17D0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.299 ETH_TYPE2_COMPARE_26_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817D4
Offset: 0x17D4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.300 ETH_TYPE2_COMPARE_27_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817D8
Offset: 0x17D8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.301 ETH_TYPE2_COMPARE_27_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817DC
Offset: 0x17DC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.302 ETH_TYPE2_COMPARE_28_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817E0
Offset: 0x17E0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.303 ETH_TYPE2_COMPARE_28_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817E4
Offset: 0x17E4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.304 ETH_TYPE2_COMPARE_29_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817E8
Offset: 0x17E8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.305 ETH_TYPE2_COMPARE_29_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817EC
Offset: 0x17EC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.306 ETH_TYPE2_COMPARE_30_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817F0
Offset: 0x17F0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.307 ETH_TYPE2_COMPARE_30_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817F4
Offset: 0x17F4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

11.1.308 ETH_TYPE2_COMPARE_31_WORD_0

Description: same as type2_compare_0_word_0
Address: 0x404817F8
Offset: 0x17F8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MASK_VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK_VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COMPARE_VALUE_TYPE2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COMPARE_VALUE_TYPE2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	MASK_VALUE	RW	RW	0	These bits can be either a 2 byte mask field or an additional 2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [7:0] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [15:8] is compared against the byte in the received frame from the selected offset+1. If bit 9 of the associated compare_word1 register is clear, these bits become a direct 2-byte mask for the 2-byte compare register in bits [31:16].
16:31	COMPARE_VALUE_TYPE2	RW	RW	0	2 byte Compare Value. If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.

11.1.309 ETH_TYPE2_COMPARE_31_WORD_1

Description: same as type2_compare_0_word_1
Address: 0x404817FC
Offset: 0x17FC
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OFFSET_VALUE [6:0]							

Bits	15	14	13	12	11	10	9	8
Name							DISABLE_MASK [9:9]	COMPARE_OFFSET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESERVED_31_10 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESERVED_31_10 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	OFFSET_VALUE	RW	RW	0	'Offset value in bytes'
7:8	COMPARE_OFFSET	RW	RW	0	'Compare byte offset. 00 : Offset from beginning of the frame. 01 : Offset from byte after Ether Type. 10 : Offset from byte following end of IP header. 11 : Offset from byte following end of TCP/UDP header' If bit 9 of the associated compare_word1 register is set, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+2 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+3. If bit 9 of the associated compare_word1 register is clear, then the byte stored in bits [23:16] is compared against the byte in the received frame from the selected offset+0 and the byte stored in bits [31:24] is compared against the byte in the received frame from the selected offset+1.
9	DISABLE_MASK	RW	RW	0	'This bit is used to control whether the compare register word_0 contains a 4-byte compare value, or a 2-byte compare value with a 2-byte mask value. 1 - 4-byte compare value 0 - 2-byte compare, 2-byte mask '
10:31	RESERVED_31_10	R	R	0	'Reserved, read as 0, ignored on write.'

12 EVTGEN

Description	Event generator
Base Address	0x403F0000
Size	0x1000
Slave Num	MMIO3 - 3

Register Name	Address	Permission	Description
EVTGEN0_CTL	0x403F0000	FULL	Control
EVTGEN0_COMP0_STATUS	0x403F0004	FULL	Comparator structures comparator 0 status
EVTGEN0_COMP1_STATUS	0x403F0008	FULL	Comparator structures comparator 1 status
EVTGEN0_COUNTER_STATUS	0x403F0010	FULL	Counter status
EVTGEN0_COUNTER	0x403F0014	FULL	Counter
EVTGEN0_RATIO_CTL	0x403F0020	FULL	Ratio control
EVTGEN0_RATIO	0x403F0024	FULL	Ratio
EVTGEN0_REF_CLOCK_CTL	0x403F0030	FULL	Reference clock control
EVTGEN0_INTR	0x403F0700	FULL	Interrupt
EVTGEN0_INTR_SET	0x403F0704	FULL	Interrupt set
EVTGEN0_INTR_MASK	0x403F0708	FULL	Interrupt mask
EVTGEN0_INTR_MASKED	0x403F070C	FULL	Interrupt masked
EVTGEN0_INTR_DPSLP	0x403F0710	FULL	DeepSleep interrupt
EVTGEN0_INTR_DPSLP_SET	0x403F0714	FULL	DeepSleep interrupt set
EVTGEN0_INTR_DPSLP_MASK	0x403F0718	FULL	DeepSleep interrupt mask
EVTGEN0_INTR_DPSLP_MASKED	0x403F071C	FULL	DeepSleep interrupt masked

12.1 COMP_STRUCT 0

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT0_COMP_CTL	0x403F0800	FULL	Comparator control
EVTGEN0_COMP_STRUCT0_COMP0	0x403F0804	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT0_COMP1	0x403F0808	FULL	Comparator 1 (DeepSleep functionality)

12.2 COMP_STRUCT 1

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT1_COMP_CTL	0x403F0820	FULL	Comparator control
EVTGEN0_COMP_STRUCT1_COMP0	0x403F0824	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT1_COMP1	0x403F0828	FULL	Comparator 1 (DeepSleep functionality)

12.3 COMP_STRUCT 2

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT2_COMP_CTL	0x403F0840	FULL	Comparator control
EVTGEN0_COMP_STRUCT2_COMP0	0x403F0844	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT2_COMP1	0x403F0848	FULL	Comparator 1 (DeepSleep functionality)

12.4 COMP_STRUCT 3

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT3_COMP_CTL	0x403F0860	FULL	Comparator control
EVTGEN0_COMP_STRUCT3_COMP0	0x403F0864	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT3_COMP1	0x403F0868	FULL	Comparator 1 (DeepSleep functionality)

12.5 COMP_STRUCT 4

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT4_COMP_CTL	0x403F0880	FULL	Comparator control
EVTGEN0_COMP_STRUCT4_COMP0	0x403F0884	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT4_COMP1	0x403F0888	FULL	Comparator 1 (DeepSleep functionality)

12.6 COMP_STRUCT 5

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT5_COMP_CTL	0x403F08A0	FULL	Comparator control
EVTGEN0_COMP_STRUCT5_COMP0	0x403F08A4	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT5_COMP1	0x403F08A8	FULL	Comparator 1 (DeepSleep functionality)

12.7 COMP_STRUCT 6

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT6_COMP_CTL	0x403F08C0	FULL	Comparator control
EVTGEN0_COMP_STRUCT6_COMP0	0x403F08C4	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT6_COMP1	0x403F08C8	FULL	Comparator 1 (DeepSleep functionality)

12.8 COMP_STRUCT 7

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT7_COMP_CTL	0x403F08E0	FULL	Comparator control
EVTGEN0_COMP_STRUCT7_COMP0	0x403F08E4	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT7_COMP1	0x403F08E8	FULL	Comparator 1 (DeepSleep functionality)

12.9 COMP_STRUCT 8

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT8_COMP_CTL	0x403F0900	FULL	Comparator control
EVTGEN0_COMP_STRUCT8_COMP0	0x403F0904	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT8_COMP1	0x403F0908	FULL	Comparator 1 (DeepSleep functionality)

12.10 COMP_STRUCT 9

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT9_COMP_CTL	0x403F0920	FULL	Comparator control
EVTGEN0_COMP_STRUCT9_COMP0	0x403F0924	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT9_COMP1	0x403F0928	FULL	Comparator 1 (DeepSleep functionality)

12.11 COMP_STRUCT 10

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT10_COMP_CTL	0x403F0940	FULL	Comparator control
EVTGEN0_COMP_STRUCT10_COMP0	0x403F0944	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT10_COMP1	0x403F0948	FULL	Comparator 1 (DeepSleep functionality)

12.12 COMP_STRUCT 11

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT11_COMP_CTL	0x403F0960	FULL	Comparator control
EVTGEN0_COMP_STRUCT11_COMP0	0x403F0964	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT11_COMP1	0x403F0968	FULL	Comparator 1 (DeepSleep functionality)

12.13 COMP_STRUCT 12

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT12_COMP_CTL	0x403F0980	FULL	Comparator control
EVTGEN0_COMP_STRUCT12_COMP0	0x403F0984	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT12_COMP1	0x403F0988	FULL	Comparator 1 (DeepSleep functionality)

12.14 COMP_STRUCT 13

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT13_COMP_CTL	0x403F09A0	FULL	Comparator control
EVTGEN0_COMP_STRUCT13_COMP0	0x403F09A4	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT13_COMP1	0x403F09A8	FULL	Comparator 1 (DeepSleep functionality)

12.15 COMP_STRUCT 14

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT14_COMP_CTL	0x403F09C0	FULL	Comparator control
EVTGEN0_COMP_STRUCT14_COMP0	0x403F09C4	FULL	Comparator 0 (Active functionality)
EVTGEN0_COMP_STRUCT14_COMP1	0x403F09C8	FULL	Comparator 1 (DeepSleep functionality)

12.16 COMP_STRUCT 15

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT15_COMP_CTL	0x403F09E0	FULL	Comparator control
EVTGEN0_COMP_STRUCT15_COMP0	0x403F09E4	FULL	Comparator 0 (Active functionality)

Register Name	Address	Permission	Description
EVTGEN0_COMP_STRUCT15_COMP1	0x403F09E8	FULL	Comparator 1 (DeepSleep functionality)

12.17 Register Details

12.17.1 EVTGEN_CTL

Description: Control
Address: 0x403F0000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLED	RW	RW	0	IP enable: '0': Disabled. All non-retention registers (command and status registers) are reset to their default value when the IP is disabled. All retention registers retain their value when the IP is disabled. '1': Enabled.
	DISABLED			0	N/A
	ENABLED			1	N/A

12.17.2 EVTGEN_COMP0_STATUS

Description: Comparator structures comparator 0 status
Address: 0x403F0004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP0_OUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP0_OUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP0_OUT	R	R	0	Active comparator 'comp0_out[]' outputs.

12.17.3 EVTGEN_COMP1_STATUS

Description: Comparator structures comparator 1 status
Address: 0x403F0008
Offset: 0x8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP1_OUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP1_OUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP1_OUT	R	R	0	DeepSleep comparator 'comp1_out_if[]' outputs (synchronized from clk_if to the IP clock).

12.17.4 EVTGEN_COUNTER_STATUS

Description: Counter status
Address: 0x403F0010
Offset: 0x10
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	R	R	0	Active counter validity: '0': Invalid. '1': Valid. The COUNTER register field INT32 is only valid when VALID is '1'. The COUNTER_STATUS and COUNTER registers are non-retention registers; i.e. the COUNTER_STATUS and COUNTER registers are reset during DeepSleep power mode. After entering the Active power mode, the Active counter is initialized with the DeepSleep counter. This initialization may take up to 1 clk_Lf cycle.

12.17.5 EVTGEN_COUNTER

Description: Counter
Address: 0x403F0014
Offset: 0x14
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INT32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INT32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INT32	R	R	Undefined	Active counter 'counter_int[31:0]' on clk_ref_div.

12.17.6 EVTGEN_RATIO_CTL

Description: Ratio control
Address: 0x403F0020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DYNAMIC_MODE [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	DYNAMIC [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:18	DYNAMIC_MODE	RW	RW	0	Weighted average calculation (only used when DYNAMIC is '1'): '0': new RATIO value = (RATIO + measurement + 1) / 2. '1': new RATIO value = (3*RATIO + measurement + 2) / 4. '2': new RATIO value = (7*RATIO + measurement + 4) / 8. '3': new RATIO value = (15*RATIO + measurement + 8) / 16. '4': new RATIO value = (31*RATIO + measurement + 16) / 32. '5': new RATIO value = (63*RATIO + measurement + 32) / 64. '6': new RATIO value = (127*RATIO + measurement + 64) / 128. '7': new RATIO value = (255*RATIO + measurement + 128) / 256. Note: 'measurement' (integer component only) is defined as: $256 * \text{'number of measured clk\_ref\_div cycles per clk\_lf cycle'}$. The RATIO value (integer and fractional component) is defined as: $256 * \text{RATIO.INT16} + \text{RATIO.FRAC8}$ ($\text{RATIO.INT16} = \text{RATIO} \gg 8$ and $\text{RATIO.FRAC8} = \text{RATIO percent 256}$).
30	DYNAMIC	RW	RW	0	Specifies if RATIO_CTL.VALID and RATIO are under SW or HW control: '0': SW control. '1': HW control. Auto calibration is used to derive the RATIO value. HW measures the number of clk_ref_div cycles per clk_lf cycle. This measurement is combined with the current ratio value to calculate a new ratio value.

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	RW	RW	0	Ratio value valid: '0': Invalid. '1': Valid. The RATIO register fields INT16 and FRAC8 are only valid when VALID is '1'.

12.17.7 EVTGEN_RATIO

Description: Ratio
Address: 0x403F0024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: This register contains a ratio value expressing the relative frequency of the DeepSleep clock `clk_lf` wrt. the Active clock `clk_ref_div`. Specifically, this registers contains the average number of `clk_ref_div` cycles per `clk_lf` cycle.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	FRAC8 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	INT16 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	INT16 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	FRAC8	RW	RW	Undefined	Fractional component of ratio value.
16:31	INT16	RW	RW	Undefined	Integer component of ratio value.

12.17.8 EVTGEN_REF_CLOCK_CTL

Description: Reference clock control
Address: 0x403F0030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT_DIV [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	INT_DIV	RW	RW	0	Divider control for clk_ref_div: '0': Divide by 1. ... '255': Divide by '256'. $Fclk\_ref\_div = Fclk\_ref / (INT\_DIV + 1)$

12.17.9 EVTGEN_INTR

Description: Interrupt
Address: 0x403F0700
Offset: 0x700
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP0	RW1C	RW1C	0	This interrupt cause field is activated (HW sets the field to '1') when a comparator 0 event is generated (Active counter 'counter_int[31:0]' becomes greater or equal to COMP0.INT[31:0]).

12.17.10 EVTGEN_INTR_SET

Description: Interrupt set

Address: 0x403F0704

Offset: 0x704

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects the INTR register. For debug purposes, SW can write a '1' to activate a specific interrupt cause (this allows for debug of the SW ISR, without relying on HW to activate the interrupt cause).

Default: The interrupt causes are deactivated when the IP is disabled (CTL.ENABLED is '0').
0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP0	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in the INTR register.

12.17.11 EVTGEN_INTR_MASK

Description: Interrupt mask
Address: 0x403F0708
Offset: 0x708
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP0	RW	RW	0	Mask bit for corresponding field in the INTR register.

12.17.12 EVTGEN_INTR_MASKED

Description: Interrupt masked
Address: 0x403F070C
Offset: 0x70C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects 'a bitwise AND' between the INTR and INTR_MASK registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP0 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP0	R	R	0	Logical and of corresponding INTR and INTR_MASK fields.

12.17.13 EVTGEN_INTR_DPSLP

Description: DeepSleep interrupt
Address: 0x403F0710
Offset: 0x710
Retention: Retained
IsDeepSleep: No
Comment: The interrupt causes are deactivated when the IP is disabled (CTL.ENABLED is '0').
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP1 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP1	RW1C	RW1C	0	This interrupt cause field is activated (HW sets the field to '1') when a comparator 1 event is generated (DeepSleep counter 'counter_int_lf[31:0]' becomes greater or equal to COMP1.INT[31:0]).

12.17.14 EVTGEN_INTR_DPSLP_SET**Description:** DeepSleep interrupt set**Address:** 0x403F0714**Offset:** 0x714**Retention:** Retained**IsDeepSleep:** No**Comment:** When read, this register reflects the INTR register. For debug purposes, SW can write a '1' to activate a specific interrupt cause (this allows for debug of the SW ISR, without relying on HW to activate the interrupt cause).**Default:** 0x0**Bit-field Table**

Bits	7	6	5	4	3	2	1	0
Name	COMP1 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP1	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in the INTR register.

12.17.15 EVTGEN_INTR_DPSLP_MASK

Description: DeepSleep interrupt mask
Address: 0x403F0718
Offset: 0x718
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP1 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP1	RW	RW	0	Mask bit for corresponding field in the INTR register.

12.17.16 EVTGEN_INTR_DPSLP_MASKED

Description: DeepSleep interrupt masked
Address: 0x403F071C
Offset: 0x71C
Retention: Retained
IsDeepSleep: No
Comment: When read, this register reflects 'a bitwise AND' between the INTR and INTR_MASK registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COMP1 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COMP1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	COMP1	R	R	0	Logical and of corresponding INTR and INTR_MASK fields.

12.17.17 COMP_STRUCT

12.17.17.1 EVTGEN_COMP_STRUCT_COMP_CTL

Description: Comparator control
Address: 0x403F0800
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						COMP1_EN [1:1]	COMP0_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							TR_OUT_EDGE [16:16]

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	COMP0_EN	RW	RW	0	Active comparator (COMP0) enable: '0': Disabled. The comparator output 'comp0_out' is '0'. '1': Enabled.
1	COMP1_EN	RW	RW	0	DeepSleep comparator (COMP1) enable: '0': Disabled. The comparator output 'comp1_out_lf' is '0'. '1': Enabled.
16	TR_OUT_EDGE	RW	RW	0	Specifies the 'tr_out' output trigger: '0': The trigger is a level sensitive trigger. The Active comparator output ('comp0_out') is reflected on 'tr_out'. '1': The trigger is an edge sensitive trigger. Activation of the Active comparator output (rising edge on 'comp0_out') results in a two cycle '1'/high pulse on 'tr_out'.
31	ENABLED	RW	RW	0	Comparator structure enable: '0': Disabled. '1': Enabled.

12.17.17.2 EVTGEN_COMP_STRUCT_COMP0

Description: Comparator 0 (Active functionality)
Address: 0x403F0804
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INT32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INT32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INT32	RW	RW	Undefined	This value is a 32-bit unsigned integer in the range [0, 2³²-1]. The comparator 'comp0_out' output is activated when the Active counter 'counter_int[31:0]' becomes greater or equal to COMP0. Note: SW must ensure that COMP_CTL.COMP_EN[0] is '0' when COMP0 is written.

12.17.17.3 EVTGEN_COMP_STRUCT_COMP1

Description: Comparator 1 (DeepSleep functionality)
Address: 0x403F0808
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INT32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INT32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INT32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INT32	RW	RW	Undefined	This value is a 32-bit unsigned integer in the range [0, 2³²-1]. The comparator 'comp1_out_if' output is activated when the DeepSleep counter 'counter_int_if[31:0]' becomes greater or equal to COMP1. Note: SW must ensure that COMP_CTL.COMP_EN[1] is '0' when COMP1 is written.

13 FAULT

Description	Fault structures
Base Address	0x40210000
Size	0x10000
Slave Num	MMIO2 - 1

13.1 STRUCT 0

Register Name	Address	Permission	Description
FAULT_STRUCT0_CTL	0x40210000	FULL	Fault control
FAULT_STRUCT0_STATUS	0x4021000C	FULL	Fault status
FAULT_STRUCT0_DATA0	0x40210010	FULL	Fault data
FAULT_STRUCT0_DATA1	0x40210014	FULL	Fault data
FAULT_STRUCT0_DATA2	0x40210018	FULL	Fault data
FAULT_STRUCT0_DATA3	0x4021001C	FULL	Fault data
FAULT_STRUCT0_PENDING0	0x40210040	FULL	Fault pending 0
FAULT_STRUCT0_PENDING1	0x40210044	FULL	Fault pending 1
FAULT_STRUCT0_PENDING2	0x40210048	FULL	Fault pending 2
FAULT_STRUCT0_MASK0	0x40210050	FULL	Fault mask 0
FAULT_STRUCT0_MASK1	0x40210054	FULL	Fault mask 1
FAULT_STRUCT0_MASK2	0x40210058	FULL	Fault mask 2
FAULT_STRUCT0_INTR	0x402100C0	FULL	Interrupt
FAULT_STRUCT0_INTR_SET	0x402100C4	FULL	Interrupt set
FAULT_STRUCT0_INTR_MASK	0x402100C8	FULL	Interrupt mask
FAULT_STRUCT0_INTR_MASKED	0x402100CC	FULL	Interrupt masked

13.2 STRUCT 1

Register Name	Address	Permission	Description
FAULT_STRUCT1_CTL	0x40210100	FULL	Fault control
FAULT_STRUCT1_STATUS	0x4021010C	FULL	Fault status
FAULT_STRUCT1_DATA0	0x40210110	FULL	Fault data
FAULT_STRUCT1_DATA1	0x40210114	FULL	Fault data
FAULT_STRUCT1_DATA2	0x40210118	FULL	Fault data
FAULT_STRUCT1_DATA3	0x4021011C	FULL	Fault data
FAULT_STRUCT1_PENDING0	0x40210140	FULL	Fault pending 0
FAULT_STRUCT1_PENDING1	0x40210144	FULL	Fault pending 1
FAULT_STRUCT1_PENDING2	0x40210148	FULL	Fault pending 2
FAULT_STRUCT1_MASK0	0x40210150	FULL	Fault mask 0
FAULT_STRUCT1_MASK1	0x40210154	FULL	Fault mask 1
FAULT_STRUCT1_MASK2	0x40210158	FULL	Fault mask 2
FAULT_STRUCT1_INTR	0x402101C0	FULL	Interrupt
FAULT_STRUCT1_INTR_SET	0x402101C4	FULL	Interrupt set
FAULT_STRUCT1_INTR_MASK	0x402101C8	FULL	Interrupt mask
FAULT_STRUCT1_INTR_MASKED	0x402101CC	FULL	Interrupt masked

13.3 STRUCT 2

Register Name	Address	Permission	Description
FAULT_STRUCT2_CTL	0x40210200	FULL	Fault control
FAULT_STRUCT2_STATUS	0x4021020C	FULL	Fault status
FAULT_STRUCT2_DATA0	0x40210210	FULL	Fault data
FAULT_STRUCT2_DATA1	0x40210214	FULL	Fault data
FAULT_STRUCT2_DATA2	0x40210218	FULL	Fault data
FAULT_STRUCT2_DATA3	0x4021021C	FULL	Fault data
FAULT_STRUCT2_PENDING0	0x40210240	FULL	Fault pending 0
FAULT_STRUCT2_PENDING1	0x40210244	FULL	Fault pending 1
FAULT_STRUCT2_PENDING2	0x40210248	FULL	Fault pending 2
FAULT_STRUCT2_MASK0	0x40210250	FULL	Fault mask 0
FAULT_STRUCT2_MASK1	0x40210254	FULL	Fault mask 1
FAULT_STRUCT2_MASK2	0x40210258	FULL	Fault mask 2
FAULT_STRUCT2_INTR	0x402102C0	FULL	Interrupt
FAULT_STRUCT2_INTR_SET	0x402102C4	FULL	Interrupt set

Register Name	Address	Permission	Description
FAULT_STRUCT2_INTR_MASK	0x402102C8	FULL	Interrupt mask
FAULT_STRUCT2_INTR_MASKED	0x402102CC	FULL	Interrupt masked

13.4 STRUCT 3

Register Name	Address	Permission	Description
FAULT_STRUCT3_CTL	0x40210300	FULL	Fault control
FAULT_STRUCT3_STATUS	0x4021030C	FULL	Fault status
FAULT_STRUCT3_DATA0	0x40210310	FULL	Fault data
FAULT_STRUCT3_DATA1	0x40210314	FULL	Fault data
FAULT_STRUCT3_DATA2	0x40210318	FULL	Fault data
FAULT_STRUCT3_DATA3	0x4021031C	FULL	Fault data
FAULT_STRUCT3_PENDING0	0x40210340	FULL	Fault pending 0
FAULT_STRUCT3_PENDING1	0x40210344	FULL	Fault pending 1
FAULT_STRUCT3_PENDING2	0x40210348	FULL	Fault pending 2
FAULT_STRUCT3_MASK0	0x40210350	FULL	Fault mask 0
FAULT_STRUCT3_MASK1	0x40210354	FULL	Fault mask 1
FAULT_STRUCT3_MASK2	0x40210358	FULL	Fault mask 2
FAULT_STRUCT3_INTR	0x402103C0	FULL	Interrupt
FAULT_STRUCT3_INTR_SET	0x402103C4	FULL	Interrupt set
FAULT_STRUCT3_INTR_MASK	0x402103C8	FULL	Interrupt mask
FAULT_STRUCT3_INTR_MASKED	0x402103CC	FULL	Interrupt masked

13.5 Register Details

13.5.1 STRUCT

13.5.1.1 FAULT_STRUCT_CTL

Description: Fault control
Address: 0x40210000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register uses DeepSleep reset. Therefore, a DeepSleep reset (possibly as a result of CTL.RESET_EN) resets this register (including setting CTL.RESET_EN to '0').
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					RESET_REQ_EN [2:2]	OUT_EN [1:1]	TR_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_EN	RW	RW	0	Trigger output enable: '0': Disabled. The trigger output 'tr_fault' is '0'. '1': Enabled. The trigger output 'tr_fault' reflects STATUS.VALID. The trigger can be used to initiate a Datawire transfer of the FAULT data (FAULT_DATA0 through FAULT_DATA3).
1	OUT_EN	RW	RW	0	IO output signal enable: '0': Disabled. The IO output signal 'fault_out' is '0'. The IO output enable signal 'fault_out_en' is '0'. '1': Enabled. The IO output signal 'fault_out' reflects STATUS.VALID. The IO output enable signal 'fault_out_en' is '1'.
2	RESET_REQ_EN	RW	RW	0	Reset request enable: '0': Disabled. '1': Enabled. The output reset request signal 'fault_reset_req' reflects STATUS.VALID. This reset causes a warm/soft/core reset. This warm/soft/core reset does not affect the fault logic STATUS, DATA0, ..., DATA3 registers (allowing for post soft reset failure analysis). The 'fault_reset_req' signals of the individual fault report structures are combined (logically OR'd) into a single SRSS 'fault_reset_req' signal.

13.5.1.2 FAULT_STRUCT_STATUS

Description: Fault status
Address: 0x4021000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: This register uses cold reset (and is NOT affected by Active or DeepSleep reset). This allows for failure analysis after a warm reset (DeepSleep reset).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	IDX [6:0]						
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	IDX	RW	RW	Undefined	The fault source index for which fault information is captured in DATA0 through DATA3. The fault information is fault source specific and described below. Note: this register field (and associated fault source data in DATA0 through DATA3) should only be considered valid, when VALID is '1'.
	MPU_0			0	Bus master 0 MPU/SMPU. DATA0[31:0]: Violating address. DATA1[0]: User read. DATA1[1]: User write. DATA1[2]: User execute. DATA1[3]: Privileged read. DATA1[4]: Privileged write. DATA1[5]: Privileged execute. DATA1[6]: Non-secure. DATA1[11:8]: Master identifier. DATA1[15:12]: Protection context identifier. DATA1[31]: '0' MPU violation; '1': SMPU violation.
	MPU_1			1	Bus master 1 MPU. See MPU_0 description.
	MPU_2			2	Bus master 2 MPU. See MPU_0 description.
	MPU_3			3	Bus master 3 MPU. See MPU_0 description.
	MPU_4			4	Bus master 4 MPU. See MPU_0 description.
	MPU_5			5	Bus master 5 MPU. See MPU_0 description.
	MPU_6			6	Bus master 6 MPU. See MPU_0 description.
	MPU_7			7	Bus master 7 MPU. See MPU_0 description.
	MPU_8			8	Bus master 8 MPU. See MPU_0 description.
	MPU_9			9	Bus master 9 MPU. See MPU_0 description.
	MPU_10			10	Bus master 10 MPU. See MPU_0 description.
	MPU_11			11	Bus master 11 MPU. See MPU_0 description.
	MPU_12			12	Bus master 12 MPU. See MPU_0 description.

Bits	Name	SW	HW	Default or Enum	Description
	MPU_13			13	Bus master 13 MPU. See MPU_0 description.
	MPU_14			14	Bus master 14 MPU. See MPU_0 description.
	MPU_15			15	Bus master 15 MPU. See MPU_0 description.
	CM7_1_TCM_C_ECC			16	Correctable ECC error in CM7_1 TCM memory. See CM7_0_TCM_C_ECC description.
	CM7_1_TCM_NC_ECC			17	Non Correctable ECC error in CM7_1 TCM memory. See CM7_0_TCM_C_ECC description.
	CM7_0_CACHE_C_ECC			18	Correctable ECC error in CM7_0 Cache memories DATA0[16:2]: location information: Tag/Data SRAM, Way, Index and line Offset, see CM7 UGRM IEBR0/DEBR0 description for details. DATA0[31]: 0=Instruction cache, 1= Data cache
	CM7_0_CACHE_NC_ECC			19	Non Correctable ECC error in CM7_0 Cache memories. See CM7_0_CACHE_C_ECC description
	CM7_1_CACHE_C_ECC			20	Correctable ECC error in CM7_1 Cache memories. See CM7_0_CACHE_C_ECC description.
	CM7_1_CACHE_NC_ECC			21	Non Correctable ECC error in CM7_1 Cache memories. See CM7_0_CACHE_C_ECC description.
	MS_PPU_4			25	Peripheral interconnect, master interface 4 PPU. See MS_PPU_0 description.
	PERI_ECC			26	Peripheral interconnect, protection structures SRAM, correctable ECC error: DATA0[10:0]: Violating address. DATA1[7:0]: Syndrome of SRAM word.
	PERI_NC_ECC			27	Peripheral interconnect, protection structures SRAM, non-correctable ECC error.
	MS_PPU_0			28	Peripheral interconnect, master interface 0 PPU. DATA0[31:0]: Violating address. DATA1[0]: User read. DATA1[1]: User write. DATA1[2]: User execute. DATA1[3]: Privileged read. DATA1[4]: Privileged write. DATA1[5]: Privileged execute. DATA1[6]: Non-secure. DATA1[11:8]: Master identifier. DATA1[15:12]: Protection context identifier. DATA1[31:28]: '0': master interface, PPU violation, '1': timeout detected, '2': bus error, other: undefined.
	MS_PPU_1			29	Peripheral interconnect, master interface 1 PPU. See MS_PPU_0 description.
	MS_PPU_2			30	Peripheral interconnect, master interface 2 PPU. See MS_PPU_0 description.
	MS_PPU_3			31	Peripheral interconnect, master interface 3 PPU. See MS_PPU_0 description.
	GROUP_FAULT_0			32	Peripheral group 0 fault detection. DATA0[31:0]: Violating address. DATA1[0]: User read. DATA1[1]: User write. DATA1[2]: User execute. DATA1[3]: Privileged read. DATA1[4]: Privileged write. DATA1[5]: Privileged execute. DATA1[6]: Non-secure. DATA1[11:8]: Master identifier. DATA1[15:12]: Protection context identifier. DATA1[31:28]: '0': decoder or peripheral bus error, other: undefined.
	GROUP_FAULT_1			33	Peripheral group 1 fault detection. See GROUP_FAULT_0 description.

Bits	Name	SW	HW	Default or Enum	Description
	GROUP_FAULT_2			34	Peripheral group 2 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_3			35	Peripheral group 3 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_4			36	Peripheral group 4 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_5			37	Peripheral group 5 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_6			38	Peripheral group 6 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_7			39	Peripheral group 7 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_8			40	Peripheral group 8 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_9			41	Peripheral group 9 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_10			42	Peripheral group 10 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_11			43	Peripheral group 11 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_12			44	Peripheral group 12 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_13			45	Peripheral group 13 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_14			46	Peripheral group 14 fault detection. See GROUP_FAULT_0 description.
	GROUP_FAULT_15			47	Peripheral group 15 fault detection. See GROUP_FAULT_0 description.
	FLASHC_MAIN_BUS_ERROR			48	Flash controller, main interface, bus error: FAULT_DATA0[26:0]: Violating address. Append 5'b00010 as most significant bits to derive 32-bit system address. FAULT_DATA1[11:8]: Master identifier.
	FLASHC_MAIN_C_ECC			49	Flash controller, main interface, correctable ECC error: DATA[26:0]: Violating address. Append 5'b00010 as most significant bits to derive 32-bit system address. DATA1[7:0]: Syndrome of 64-bit word (at address offset 0x00). DATA1[15:8]: Syndrome of 64-bit word (at address offset 0x08). DATA1[23:16]: Syndrome of 64-bit word (at address offset 0x10). DATA1[31:24]: Syndrome of 64-bit word (at address offset 0x18).
	FLASHC_MAIN_NC_ECC			50	Flash controller, main interface, non-correctable ECC error. See FLASHC_MAIN_C_ECC description.
	FLASHC_WORK_BUS_ERROR			51	Flash controller, work interface, bus error. See FLASHC_MAIN_BUS_ERROR description.
	FLASHC_WORK_C_ECC			52	Flash controller, work interface, correctable ECC error: DATA0[26:0]: Violating address. Append 5'b00010 as most significant bits to derive 32-bit system address. DATA1[6:0]: Syndrome of 32-bit word.
	FLASHC_WORK_NC_ECC			53	Flash controller, work interface, non-correctable ECC error. See FLASHC_WORK_C_ECC description.

Bits	Name	SW	HW	Default or Enum	Description
	FLASHC_CM0_CA_C_ECC			54	Flash controller, CM0+ cache, correctable ECC error: DATA0[26:0]: Violating address. DATA1[6:0]: Syndrome of 32-bit SRAM word (at address offset 0x0). DATA1[14:8]: Syndrome of 32-bit SRAM word (at address offset 0x4). DATA1[22:16]: Syndrome of 32-bit SRAM word (at address offset 0x8). DATA1[30:24]: Syndrome of 32-bit SRAM word (at address offset 0xc).
	FLASHC_CM0_CA_NC_ECC			55	Flash controller, CM0+ cache, non-correctable ECC error. See FLASHC_CM0_CA_C_ECC description.
	CM7_0_TCM_C_ECC			56	Correctable ECC error in CM7_0 TCM memory DATA0[23:2]: Violating address. DATA1[7:0]: Syndrome of code word (at address offset 0x0). DATA1[31:30]: 0= ITCM, 2=D0TCM, 3=D1TCM
	CM7_0_TCM_NC_ECC			57	Non Correctable ECC error in CM7_0 TCM memory. See CM7_0_TCM_C_ECC description.
	RAMC0_C_ECC			58	System SRAM 0 correctable ECC error: DATA0[31:0]: Violating address. DATA1[6:0]: Syndrome of 32-bit SRAM code word.
	RAMC0_NC_ECC			59	System SRAM 0 non-correctable ECC error. See RAMC0_C_ECC description.
	RAMC1_C_ECC			60	System SRAM 1 correctable ECC error. See RAMC0_C_ECC description.
	RAMC1_NC_ECC			61	System SRAM 1 non-correctable ECC error. See RAMC0_C_ECC description.
	RAMC2_C_ECC			62	System SRAM 2 correctable ECC error. See RAMC0_C_ECC description.
	RAMC2_NC_ECC			63	System SRAM 2 non-correctable ECC error. See RAMC0_C_ECC description.
	CRYPTO_C_ECC			64	Cryptography SRAM correctable ECC error. DATA0[31:0]: Violating address. DATA1[6:0]: Syndrome of Least Significant 32-bit SRAM. DATA1[14:8]: Syndrome of Most Significant 32-bit SRAM.
	CRYPTO_NC_ECC			65	Cryptography SRAM non-correctable ECC error. See CRYPTO_C_ECC description.
	DW0_C_ECC			70	DataWire 0 SRAM 1 correctable ECC error: DATA0[11:0]: Violating DW SRAM address (word address, assuming byte addressable). DATA1[6:0]: Syndrome of 32-bit SRAM code word.
	DW0_NC_ECC			71	DataWire 0 SRAM 1 non-correctable ECC error. See DW0_C_ECC description.
	DW1_C_ECC			72	DataWire 1 SRAM 1 correctable ECC error. See DW0_C_ECC description.
	DW1_NC_ECC			73	DataWire 1 SRAM 1 non-correctable ECC error. See DW0_C_ECC description.
	FM_SRAM_C_ECC			74	eCT Flash SRAM (for embedded operations) correctable ECC error: DATA0[15:0]: Address location in the eCT Flash SRAM. DATA1[6:0]: Syndrome of 32-bit SRAM word.
	FM_SRAM_NC_ECC			75	eCT Flash SRAM non-correctable ECC error: See FM_SRAM_C_ECC description.

Bits	Name	SW	HW	Default or Enum	Description
	CAN0_C_ECC			80	CAN controller 0 MRAM correctable ECC error: DATA0[15:0]: Violating address. DATA0[22:16]: ECC violating data[38:32] from MRAM. DATA0[27:24]: Master ID: 0-7 = CAN channel ID within mxttcanfd cluster, 8 = AHB I/F DATA1[31:0]: ECC violating data[31:0] from MRAM.
	CAN0_NC_ECC			81	CAN controller 0 MRAM non-correctable ECC error: DATA0[15:0]: Violating address. DATA0[22:16]: ECC violating data[38:32] from MRAM (not for Address Error). DATA0[27:24]: Master ID: 0-7 = CAN channel ID within mxttcanfd cluster, 8 = AHB I/F DATA0[30]: Write access, only possible for Address Error DATA0[31]: Address Error: a CAN channel did an MRAM access above MRAM_SIZE DATA1[31:0]: ECC violating data[31:0] from MRAM (not for Address Error).
	CAN1_C_ECC			82	CAN controller 1 MRAM correctable ECC error. See CAN0_C_ECC description.
	CAN1_NC_ECC			83	CAN controller 1 MRAM non-correctable ECC error. See CAN0_NC_ECC description.
	VIDEOSS_VRP0			84	Video Ram Protection Unit 0 fault detection. DATA0[31:0]: Violating address. DATA1[0]: User read. DATA1[1]: User write. DATA1[2]: User execute. DATA1[3]: Privileged read. DATA1[4]: Privileged write. DATA1[5]: Privileged execute. DATA1[6]: Non-secure. DATA1[11:8]: Master identifier. DATA1[15:12]: Protection context identifier. DATA1[31:28]: '0': decoder or peripheral bus error, other: undefined.
	VIDEOSS_VRP1			85	Video Ram Protection Unit 1 fault detection. See VIDEOSS_VRP0 description.
	VIDEOSS_VRP2			86	Video Ram Protection Unit 2 fault detection. See VIDEOSS_VRP0 description.
	VIDEOSS_VRP3			87	Video Ram Protection Unit 3 fault detection. See VIDEOSS_VRP0 description.
	VIDEOSS_VRP4			88	Video Ram Protection Unit 4 fault detection. See VIDEOSS_VRP0 description.
	VIDEOSS_VRP5			89	Video Ram Protection Unit 5 fault detection. See VIDEOSS_VRP0 description.
	SRSS_CSV			90	SRSS Clock SuperVisor (CSV) violation detected. Multiple CSV can detect a violation at the same time. DATA0[15:0]: clk_hf* root CSV violation flags. DATA0[24]: clk_ref CSV violation flag (reference clock for clk_hf CSVs) DATA0[25]: clk_lf CSV violation flag DATA0[26]: clk_hvilo CSV violation flag
	SRSS_SSV			91	SRSS Clock SuperVisor (CSV) violation detected. Multiple CSV can detect a violation at the same time. DATA0[0]: BOD on VDDA DATA[1]: OVD on VDDA DATA[16]: LVD/HVD #1 DATA0[17]: LVD/HVD #2

Bits	Name	SW	HW	Default or Enum	Description
	SRSS_MCWDT0			92	SRSS Multi-Counter Watch Dog Timer (MCWDT) #0 violation detected. Multiple counters can detect a violation at the same time. DATA0[0]: MCWDT subcounter 0 LOWER_LIMIT DATA0[1]: MCWDT subcounter 0 UPPER_LIMIT DATA0[2]: MCWDT subcounter 1 LOWER_LIMIT DATA0[3]: MCWDT subcounter 1 UPPER_LIMIT
	SRSS_MCWDT1			93	SRSS Multi-Counter Watch Dog Timer (MCWDT) #1 violation detected. See SRSS_MCWDT0 description.
	SRSS_MCWDT2			94	SRSS Multi-Counter Watch Dog Timer (MCWDT) #2 violation detected. See SRSS_MCWDT0 description.
	SRSS_MCWDT3			95	SRSS Multi-Counter Watch Dog Timer (MCWDT) #3 violation detected. See SRSS_MCWDT0 description.
31	VALID	RW	RW	0	Valid indication: '0': Invalid. '1': Valid. STATUS.IDX, DATA0, ..., DATA3 specify the fault. Note: Typically, HW sets this field to '1' (on an activated HW fault source that is 'enabled' by the MASK registers) and SW clears this field to '0' (typically by boot code SW (after a warm system reset, when the fault is handled). In this typical use case scenario, the HW source fault data is simultaneously captured into DATA0, ..., DATA3 when the VALID field is set to '1'. An exceptional SW use case scenario is identified as well. In this scenario, SW sets this field to '1' with a fault source index different to one of the defined HW fault sources. SW update is not restricted by the MASK registers). In both use case scenarios, the following holds: - STATUS.IDX, DATA0, ..., DATA3 can only be written when STATUS.VALID is '0'; the fault structure is not in use yet. Writing STATUS.VALID to '1' effectively locks the fault structure (until SW clears STATUS.VALID to '0'). This restriction requires a SW update to sequentially update the DATA registers followed by an update of the STATUS register. Note: For the exceptional SW use case, sequential updates to the DATA and STATUS registers may be 'interrupted' by a HW fault capture. In this case, the SW DATA register updates are overwritten by the HW update (and the STATUS.IDX field will reflect the HW capture)

13.5.1.3 FAULT_STRUCT_DATA

Description: Fault data
Address: 0x40210010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: The DATA registers capture fault information.

These register use cold reset (and are NOT affected by Active or DeepSleep reset). This allows for failure analysis after a warm reset (DeepSleep reset).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	Undefined	Captured fault source data. Note: the DATA registers can only be written when STATUS.VALID is '0'. Note: the fault source index STATUS.IDX specifies the format of the DATA registers.

13.5.1.4 FAULT_STRUCT_PENDING0

Description: Fault pending 0

Address: 0x40210040

Offset: 0x40

Retention: Not Retained

IsDeepSleep: No

Comment: The PENDING0, PENDING1, PENDING2 registers specify pending (not captured) fault sources. The fault source for which data is captured in DATA0 through DATA3 and which is validated by STATUS.VALID and identified by STATUS.IDX is NOT included in this list of pending fault sources. When a fault source is captured, its corresponding bit field in PENDING0/1/2 is set to '0'.

Note that the pending fault sources are the same for ALL fault structures; i.e. these registers are NOT qualified by the fault structure specific MASK0, MASK1 and MASK2 registers.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	R	R	Undefined	This field specifies the following sources: Bit 0: CM0 MPU. Bit 1: CRYPTO MPU. Bit 2: DW 0 MPU. Bit 3: DW 1 MPU. Bit 4: DMA controller MPU. ... Bit 15: DAP MPU. Bit 16: CM4 system bus MPU. Bit 17: CM4 code bus MPU (for non FLASH controller accesses). Bit 18: CM4 code bus MPU (for FLASH controller accesses).

13.5.1.5 FAULT_STRUCT_PENDING1

Description: Fault pending 1
Address: 0x40210044
Offset: 0x44
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	R	R	Undefined	This field specifies the following sources: Bit 0: Peripheral group 0 PPU. Bit 1: Peripheral group 1 PPU. Bit 2: Peripheral group 2 PPU. Bit 3: Peripheral group 3 PPU. Bit 4: Peripheral group 4 PPU. Bit 5: Peripheral group 5 PPU. Bit 6: Peripheral group 6 PPU. Bit 7: Peripheral group 7 PPU. ... Bit 15: Peripheral group 15 PPU. Bit 16 - 31: See STATUS register.

13.5.1.6 FAULT_STRUCT_PENDING2

Description: Fault pending 2
Address: 0x40210048
Offset: 0x48
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	R	R	Undefined	This field specifies the following sources: Bit 0 - 31: See STATUS register.

13.5.1.7 FAULT_STRUCT_MASK0

Description: Fault mask 0

Address: 0x40210050

Offset: 0x50

Retention: Retained

IsDeepSleep: No

Comment: The MASK0, MASK1, MASK2 registers specify 'enables' for fault sources. Only 'enabled' fault sources will be captured by this fault structure (and result in STATUS.VALID and INTR.FAULT being set to '1'). When a fault source is captured, its corresponding bit field in PENDING0/1/2 is set to '0'.

When multiple fault structures are present and the mask fields of the fault structures overlap (the same source is 'enabled' for multiple fault structures), an overlapping enabled pending fault source is captured by a single fault structure that has not captured a fault (the fault structure with the lowest index has precedence).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	RW	RW	0	Fault source enables: Bits 31-0: Fault sources 31 to 0.

13.5.1.8 FAULT_STRUCT_MASK1

Description: Fault mask 1
Address: 0x40210054
Offset: 0x54
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	RW	RW	0	Fault source enables: Bits 31-0: Fault sources 63 to 32.

13.5.1.9 FAULT_STRUCT_MASK2

Description: Fault mask 2
Address: 0x40210058
Offset: 0x58
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SOURCE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SOURCE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SOURCE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SOURCE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	SOURCE	RW	RW	0	Fault source enables: Bits 31-0: Fault sources 95 to 64.

13.5.1.10 FAULT_STRUCT_INTR

Description: Interrupt
Address: 0x402100C0
Offset: 0xC0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							FAULT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FAULT	RW1C	RW1C	0	This interrupt cause field is activated (HW sets the field to '1') when an enabled (MASK0/MASK1/MASK2) pending fault source is captured: - STATUS.VALID is set to '1'. - STATUS.IDX specifies the fault source index. - DATA0 through DATA3 captures the fault source data. SW writes a '1' to this field to clear the interrupt cause to '0'. SW clear STATUS.VALID to '0' to enable capture of the next fault. Note that when there is an enabled pending fault source, the pending fault source is captured immediately and INTR.FAULT is immediately activated (set to '1').

13.5.1.11 FAULT_STRUCT_INTR_SET

Description: Interrupt set
Address: 0x402100C4
Offset: 0xC4
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the INTR register. For debug purposes, SW can write a '1' to activate a specific interrupt cause (this allows for debug of the SW ISR, without relying on HW to activate the interrupt cause).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							FAULT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FAULT	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in the INTR register.

13.5.1.12 FAULT_STRUCT_INTR_MASK

Description: Interrupt mask
Address: 0x402100C8
Offset: 0xC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							FAULT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FAULT	RW	RW	0	Mask bit for corresponding field in the INTR register.

13.5.1.13 FAULT_STRUCT_INTR_MASKED

Description: Interrupt masked
Address: 0x402100CC
Offset: 0xCC
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects 'a bitwise AND' between the INTR and INTR_MASK registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							FAULT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FAULT	R	R	0	Logical and of corresponding INTR and INTR_MASK fields.

14 FLASHC

Description Flash controller
Base Address 0x40240000
Size 0x10000
Slave Num MMIO2 - 4

Register Name	Address	Permission	Description
FLASHC_FLASH_CTL	0x40240000	FULL	Control
FLASHC_FLASH_PWR_CTL	0x40240004	FULL	Flash power control
FLASHC_FLASH_CMD	0x40240008	FULL	Command
FLASHC_ECC_CTL	0x402402A0	READ	ECC control
FLASHC_FM_SRAM_ECC_CTL0	0x402402B0	READ	eCT Flash SRAM ECC control 0
FLASHC_FM_SRAM_ECC_CTL1	0x402402B4	READ	eCT Flash SRAM ECC control 1
FLASHC_FM_SRAM_ECC_CTL2	0x402402B8	READ	eCT Flash SRAM ECC control 2
FLASHC_FM_SRAM_ECC_CTL3	0x402402BC	READ	eCT Flash SRAM ECC control 3
FLASHC_CM0_CA_CTL0	0x40240400	FULL	CM0+ cache control
FLASHC_CM0_CA_CTL1	0x40240404	FULL	CM0+ cache control
FLASHC_CM0_CA_CTL2	0x40240408	FULL	CM0+ cache control
FLASHC_CM0_CA_STATUS0	0x40240440	FULL	CM0+ cache status 0
FLASHC_CM0_CA_STATUS1	0x40240444	FULL	CM0+ cache status 1
FLASHC_CM0_CA_STATUS2	0x40240448	FULL	CM0+ cache status 2
FLASHC_CM0_STATUS	0x40240460	FULL	CM0+ interface status
FLASHC_CM7_0_STATUS	0x402404E0	FULL	CM7 #0 interface status
FLASHC_CM7_1_STATUS	0x40240560	FULL	CM7 #1 interface status
FLASHC_CRYPT0_BUFF_CTL	0x40240580	FULL	Cryptography buffer control
FLASHC_DW0_BUFF_CTL	0x40240600	FULL	Datawire 0 buffer control
FLASHC_DW1_BUFF_CTL	0x40240680	FULL	Datawire 1 buffer control
FLASHC_DMAL_BUFF_CTL	0x40240700	FULL	DMA controller buffer control
FLASHC_SLOW0_MS_BUFF_CTL	0x40240780	FULL	Slow external master 0 buffer control
FLASHC_SLOW1_MS_BUFF_CTL	0x40240800	FULL	Slow external master 1 buffer control

14.1 FM_CTL_ECT

Register Name	Address	Permission	Description
FLASHC_FM_CTL	0x4024F000	NO-ACCESS	Flash Macro Control
FLASHC_FM_CODE_MARGIN	0x4024F004	NO-ACCESS	Flash Macro Margin Mode on Code Flash
FLASHC_FM_ADDR	0x4024F008	NO-ACCESS	Flash Macro Address
FLASHC_INTR	0x4024F020	NO-ACCESS	Interrupt
FLASHC_INTR_SET	0x4024F024	NO-ACCESS	Interrupt Set
FLASHC_INTR_MASK	0x4024F028	NO-ACCESS	Interrupt Mask
FLASHC_INTR_MASKED	0x4024F02C	NO-ACCESS	Interrupt Masked
FLASHC_ECC_OVERRIDE	0x4024F030	NO-ACCESS	ECC Data In override information and control bits
FLASHC_FM_DATA	0x4024F040	NO-ACCESS	Flash macro data_in[31 to 0] both Code and Work Flash
FLASHC_BOOKMARK	0x4024F064	NO-ACCESS	Bookmark register - keeps the current FW HV seq
FLASHC_MAIN_FLASH_SAFETY	0x4024F400	FULL	Main (Code) Flash Security enable
FLASHC_STATUS	0x4024F404	FULL	Status read from Flash Macro
FLASHC_WORK_FLASH_SAFETY	0x4024F500	FULL	Work Flash Security enable

14.2 Register Details

14.2.1 FLASHC_FLASH_CTL

Description: Control
Address: 0x40240000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				WS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		WORK_BANK_MODE [13:13]	MAIN_BANK_MODE [12:12]	None [11:10]		WORK_MAP [9:9]	MAIN_MAP [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	WORK_ERR_SILENT [22:22]	WORK_ECC_INJ_EN [21:21]	WORK_ECC_EN [20:20]	None [19:19]	MAIN_ERR_SILENT [18:18]	MAIN_ECC_INJ_EN [17:17]	MAIN_ECC_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							WORK_SEQ_RD_EN [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	WS	RW	RW	0	FLASH macro wait states (same for main and work interfaces): '0': 0 wait states. ... '15': 15 wait states
8	MAIN_MAP	RW	RW	0	N/A
9	WORK_MAP	RW	RW	0	N/A
12	MAIN_BANK_MODE	RW	RW	0	N/A
13	WORK_BANK_MODE	RW	RW	0	N/A
16	MAIN_ECC_EN	RW	RW	0	N/A
17	MAIN_ECC_INJ_EN	RW	RW	0	N/A

Bits	Name	SW	HW	Default or Enum	Description
18	MAIN_ERR_SILENT	RW	RW	0	Specifies bus transfer behavior for a non-recoverable error on the FLASH macro main interface (either a non-correctable ECC error or a FLASH macro main interface internal error): 0: Bus transfer has a bus error. 1: Bus transfer does NOT have a bus error; i.e. the error is 'silent' In either case, the erroneous FLASH macro data is returned by the bus master interface. The erroneous data is NOT placed in a bus master interface's cache and/or buffer. This field is ONLY used by CPU (or debug i.e. SYS_AP/CM0_AP/CM7_0/1_AP) bus transfers. Non-CPU bus transfers always have a bus transfer with a bus error, in case of a non-recoverable error. Note: All CPU bus masters have dedicated status registers (CM0_STATUS, CM7_0_STATUS and CM7_1_STATUS) to register the occurrence of FLASH macro main interface internal errors (non-correctable ECC errors are NOT registered). Note: fault reporting can be used to identify the error that occurred: - FLASH macro main interface internal error. - FLASH macro main interface non-recoverable ECC error. - FLASH macro main interface recoverable ECC error.
20	WORK_ECC_EN	RW	RW	0	N/A
21	WORK_ECC_INJ_EN	RW	RW	0	N/A
22	WORK_ERR_SILENT	RW	RW	0	Specifies bus transfer behavior for a non-recoverable error on the FLASH macro work interface (either a non-correctable ECC error or a FLASH macro work interface internal error): 0: Bus transfer has a bus error. 1: Bus transfer does NOT have a bus error; i.e. the error is 'silent' In either case, the erroneous FLASH macro data is returned by the bus master interface. The erroneous data is NOT placed in a bus master interface's cache and/or buffer. This field is ONLY used by CPU (or debug i.e. SYS_AP/CM0_AP/CM7_0/1_AP) bus transfers. Non-CPU bus transfers always have a bus transfer with a bus error, in case of a non-recoverable error. Note: All CPU bus masters have dedicated status registers (CM0_STATUS, CM7_0_STATUS and CM7_1_STATUS) to register the occurrence of FLASH macro work interface internal errors (non-correctable ECC errors are NOT registered). Note: fault reporting can be used to identify the error that occurred: - FLASH macro work interface internal error. - FLASH macro work interface non-recoverable ECC error. - FLASH macro work interface recoverable ECC error.

Bits	Name	SW	HW	Default or Enum	Description
24	WORK_SEQ_RD_EN	RW	RW	1	Enable sequential read mode for Work Flash for read accesses on the AXI port. 0: Sequential read mode for Work Flash is disabled. 1: Sequential read mode for Work Flash is enabled. This speeds up subsequent AXI read accesses to the same page (64 bytes) of the Work Flash. Setting this field to '1' has a side effect on the round-robin arbitration of the Work Flash macro between the different ports. When this field is set to '1', then as soon as the arbitration of the Work Flash is given to the AXI port, it is not released before the current AXI read burst either has been completed or leaves the current Work Flash page (64 bytes). This means that AHB masters accessing the Work Flash that have the same priority as the AXI port will not get their fair share of the Work Flash bandwidth. While an AHB master can perform one Work Flash access per round-robin cycle (4 bytes), an AXI master can read a whole AXI burst, or up to the next Work Flash page boundary. So if this field is set to '1', and an AHB master requires a high Work Flash bandwidth, then it should have a higher priority than the AXI masters accessing the Work Flash.

14.2.2 FLASHC_FLASH_PWR_CTL

Description: Flash power control

Address: 0x40240004

Offset: 0x4

Retention: Retained

IsDeepSleep: No

Comment: This register controls Flash memory power control input pins 'enable' and 'enable_hv'. Flash memory can be turned OFF through SW in LPACTIVE power mode by making ENABLE=0 and ENABLE_HV=0. The wakeup time of the Flash memory is 10us (Twake1). So, SW has to wait for 10us to read from Flash after turning the Flash memory ON through this register.

Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						ENABLE_HV [1:1]	ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLE	RW	RW	1	Controls 'enable' pin of the Flash memory.
1	ENABLE_HV	RW	RW	1	Controls 'enable_hv' pin of the Flash memory.

14.2.3 FLASHC_FLASH_CMD

Description: Command
Address: 0x40240008
Offset: 0x8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						BUFF_INV [1:1]	INV [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INV	RW1S	RW1S	0	Invalidation of ALL caches (for CM0+) and ALL buffers. SW writes a '1' to clear the caches. HW sets this field to '0' when the operation is completed. The operation takes a maximum of three clock cycles on the slowest of the clk_slow and clk_fast clocks. The caches LRU structures are also reset to their default state.
1	BUFF_INV	RW1S	RW1S	0	Invalidation of ALL buffers (does not invalidate the caches). SW writes a '1' to clear the buffers. HW sets this field to '0' when the operation is completed. The operation takes a maximum of three clock cycles on the slowest of the clk_slow and clk_fast clocks. Note: the caches only capture FLASH macro main array data. Therefore, invalidating just the buffers (BUFF_INV) does not invalidate captures main array data in the caches.

14.2.4 FLASHC_ECC_CTL

Description: ECC control
Address: 0x402402A0
Offset: 0x2A0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORD_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	WORD_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WORD_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PARITY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	WORD_ADDR	RW	RW	0	N/A
24:31	PARITY	RW	RW	0	N/A

14.2.5 FLASHC_FM_SRAM_ECC_CTL0

Description: eCT Flash SRAM ECC control 0
Address: 0x402402B0
Offset: 0x2B0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECC_INJ_DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ECC_INJ_DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ECC_INJ_DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ECC_INJ_DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ECC_INJ_DATA	RW	RW	0	32-bit data for ECC error injection test of eCT Flash SRAM ECC logic.

14.2.6 FLASHC_FM_SRAM_ECC_CTL1

Description: eCT Flash SRAM ECC control 1
Address: 0x402402B4
Offset: 0x2B4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7] ECC_INJ_PARITY [6:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	ECC_INJ_PARITY	RW	RW	0	7-bit parity for ECC error injection test of eCT Flash SRAM ECC logic.

14.2.7 FLASHC_FM_SRAM_ECC_CTL2

Description: eCT Flash SRAM ECC control 2
Address: 0x402402B8
Offset: 0x2B8
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CORRECTED_DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CORRECTED_DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CORRECTED_DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CORRECTED_DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CORRECTED_DATA	R	R	0	32-bit corrected data output of the ECC syndrome logic.

14.2.8 FLASHC_FM_SRAM_ECC_CTL3

Description: eCT Flash SRAM ECC control 3
Address: 0x402402BC
Offset: 0x2BC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			ECC_INJ_EN [4:4]	None [3:1]			ECC_ENABLE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							ECC_TEST_FAIL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ECC_ENABLE	RW	RW	1	ECC generation/check enable for eCT Flash SRAM memory.
4	ECC_INJ_EN	RW	RW	0	eCT Flash SRAM ECC error injection test enable. Follow the steps below for ECC logic test: 1. Write corrupted or uncorrupted 39-bit data to FM_SRAM_ECC_CTL0/1 registers. 2. Set the ECC_INJ_EN bit to '1'. 3. Confirm that the bit ECC_TEST_FAIL is '0'. If this is not the case, start over at item 1 because the eCT Flash was not idle. 4. Check the corrected data in FM_SRAM_ECC_CTL2. 5. Confirm that fault was reported to fault structure, and check syndrome (only applicable if corrupted data was written in step 1). 6. If not finished, start over at 1 with different data.
8	ECC_TEST_FAIL	R	R	0	Status of ECC test. 1: ECC test failed because eCT Flash macro is busy and using the SRAM. 0: ECC was performed.

14.2.9 FLASHC_CM0_CA_CTL0

Description: CM0+ cache control
Address: 0x40240400
Offset: 0x400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xC0000001

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						RAM_ECC_INJ_EN [1:1]	RAM_ECC_EN [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						WAY [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	CA_EN [31:31]	PREF_EN [30:30]	None [29:27]			SET_ADDR [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RAM_ECC_EN	RW	RW	1	Enable ECC checking for cache accesses: 0: Disabled. 1: Enabled.
1	RAM_ECC_INJ_EN	RW	RW	0	Enable error injection for cache. When '1', the parity (ECC_CTL.PARITY[6:0]) is used when a refill is done from the FLASH macro to the ECC_CTL.WORD_ADDR[24:0] word address.
16:17	WAY	RW	RW	0	Specifies the cache way for which cache information is provided in CM0_CA_STATUS0/1/2.
24:26	SET_ADDR	RW	RW	0	Specifies the cache set for which cache information is provided in CM0_CA_STATUS0/1/2.
30	PREF_EN	RW	RW	1	Prefetch enable: 0: Disabled. 1: Enabled. Prefetching requires the cache to be enabled; i.e. ENABLED is '1'.
31	CA_EN	RW	RW	1	Cache enable: 0: Disabled. The cache tag valid bits are reset to '0's and the cache LRU information is set to '1's (making way 0 the LRU way and way 3 the MRU way). 1: Enabled.G269

14.2.10 FLASHC_CM0_CA_CTL1

Description: CM0+ cache control

Address: 0x40240404

Offset: 0x404

Retention: Retained

IsDeepSleep: No

Comment: This register controls the CM0 Cache SRAM power states. CM0 Cache SRAM consists of a single power partition.

Default: 0xFA050003

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						PWR_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VECTKEYSTAT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VECTKEYSTAT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	PWR_MODE	RW	RW	3	Specifies power mode for CM0 cache. The following sequence should be followed for turning OFF/ON the cache SRAM. Turn OFF sequence: a) Write CM0_CA_CTL0 to disable cache. b) Write CM0_CA_CTL1 to turn OFF cache SRAM. Turn ON sequence: a) Write CM0_CA_CTL1 to turn ON cache SRAM. b) Delay to allow power up of cache SRAM. Delay should be at a minimum of CM0_CA_CTL2.PWRUP_DELAY CLK_SLOW clock cycles. c) Write CM0_CA_CTL0 to enable cache.
	OFF			0	Power OFF the CM0 cache SRAM.
	RESERVED			1	Undefined
	RETAINED			2	Put CM0 cache SRAM in retained mode.
	ENABLED			3	Enable/Turn ON the CM0 cache SRAM.
16:31	VECTKEYSTAT	R	R	64005	Register key (to prevent accidental writes). - Should be written with a 0x05fa key value for the write to take effect. - Always reads as 0xfa05. Note: Although the SW attribute for this field says "R", SW need to write the key 0x05fa in this field for this register write to happen. This is a built in protection provided to prevent accidental writes from SW.

14.2.11 FLASHC_CM0_CA_CTL2

Description: CM0+ cache control
Address: 0x40240408
Offset: 0x408
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x12C

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PWRUP_DELAY [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PWRUP_DELAY [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	PWRUP_DELAY	RW	RW	300	Number clock cycles delay needed after power domain power up

14.2.12 FLASHC_CM0_CA_STATUS0

Description: CM0+ cache status 0
Address: 0x40240440
Offset: 0x440
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALID32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALID32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALID32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALID32	R	R	0	Sixteen valid bits of the cache line specified by CM0_CA_CTL.WAY and CM0_CA_CTL.SET_ADDR.

14.2.13 FLASHC_CM0_CA_STATUS1

Description: CM0+ cache status 1
Address: 0x40240444
Offset: 0x444
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TAG [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TAG [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TAG [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TAG [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TAG	R	R	Undefined	Cache line address of the cache line specified by CM0_CA_CTL.WAY and CM0_CA_CTL.SET_ADDR.

14.2.14 FLASHC_CM0_CA_STATUS2

Description: CM0+ cache status 2
Address: 0x40240448
Offset: 0x448
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		LRU [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	LRU	R	R	Undefined	Six bit LRU representation of the cache set specified by CM0_CA_CTL.SET_ADDR. The encoding of the field is as follows ('X_LRU_Y' indicates that way X is Less Recently Used than way Y): Bit 5: 0_LRU_1: way 0 less recently used than way 1. Bit 4: 0_LRU_2. Bit 3: 0_LRU_3. Bit 2: 1_LRU_2. Bit 1: 1_LRU_3. Bit 0: 2_LRU_3.

14.2.15 FLASHC_CM0_STATUS

Description: CM0+ interface status
Address: 0x40240460
Offset: 0x460
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						WORK_INT ERNAL_ERR [1:1]	MAIN_INTE RNAL_ERR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MAIN_INTERNAL_ERR	RW1C	RW1C	0	Specifies/registers the occurrence of a FLASH macro main interface internal error (typically the result of a read access while a program erase operation is ongoing) as a result of a CM0+ (or debug access via SYS_AP/CM0_AP) access. SW clears this field to '0'. HW sets this field to '1' on a FLASH macro main interface internal error. Typically, SW reads this field after a code section to detect the occurrence of an error. Note: this field is independent of FLASH_CTL.MAIN_ERR_SILENT.
1	WORK_INTERNAL_ERR	RW1C	RW1C	0	See CM0_STATUS.MAIN_INTERNAL_ERROR.

14.2.16 FLASHC_CM7_0_STATUS

Description: CM7 #0 interface status
Address: 0x402404E0
Offset: 0x4E0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						WORK_INT ERNAL_ERR [1:1]	MAIN_INTE RNAL_ERR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MAIN_INTERNAL_ERR	RW1C	RW1C	0	Specifies/registers the occurrence of a FLASH macro main interface internal error (typically the result of a read access while a program erase operation is ongoing) as a result of a CM7_0 (or debug access via SYS_AP/CM7_0_AP) access. SW clears this field to '0'. HW sets this field to '1' on a FLASH macro main interface internal error. Typically, SW reads this field after a code section to detect the occurrence of an error. Note: this field is independent of FLASH_CTL.MAIN_ERR_SILENT.
1	WORK_INTERNAL_ERR	RW1C	RW1C	0	See CM7_0_STATUS.MAIN_INTERNAL_ERROR.

14.2.17 FLASHC_CM7_1_STATUS

Description: CM7 #1 interface status
Address: 0x40240560
Offset: 0x560
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						WORK_INT ERNAL_ERR [1:1]	MAIN_INTE RNAL_ERR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MAIN_INTERNAL_ERR	RW1C	RW1C	0	Specifies/registers the occurrence of a FLASH macro main interface internal error (typically the result of a read access while a program erase operation is ongoing) as a result of a CM7_1 (or debug access via SYS_AP/CM7_1_AP) access. SW clears this field to '0'. HW sets this field to '1' on a FLASH macro main interface internal error. Typically, SW reads this field after a code section to detect the occurrence of an error. Note: this field is independent of FLASH_CTL.MAIN_ERR_SILENT.
1	WORK_INTERNAL_ERR	RW1C	RW1C	0	See CM7_1_STATUS.MAIN_INTERNAL_ERROR.

14.2.18 FLASHC_CRYPT0_BUFF_CTL

Description: Cryptography buffer control
Address: 0x40240580
Offset: 0x580
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	Prefetch enable: 0: Disabled. 1: Enabled.

14.2.19 FLASHC_DW0_BUFF_CTL

Description: Datawire 0 buffer control
Address: 0x40240600
Offset: 0x600
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	See CRYPTO_BUFF_CTL.

14.2.20 FLASHC_DW1_BUFF_CTL

Description: Datawire 1 buffer control
Address: 0x40240680
Offset: 0x680
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	See CRYPTO_BUFF_CTL.

14.2.21 FLASHC_DMACH_BUFF_CTL

Description: DMA controller buffer control
Address: 0x40240700
Offset: 0x700
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	See CRYPTO_BUFF_CTL.

14.2.22 FLASHC_SLOW0_MS_BUFF_CTL

Description: Slow external master 0 buffer control
Address: 0x40240780
Offset: 0x780
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	See CRYPTO_BUFF_CTL.

14.2.23 FLASHC_SLOW1_MS_BUFF_CTL

Description: Slow external master 1 buffer control
Address: 0x40240800
Offset: 0x800
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	PREF_EN [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	PREF_EN	RW	RW	1	See CRYPTO_BUFF_CTL.

14.2.24 FM_CTL_ECT

14.2.24.1 FLASHC_FM_CTL

Description: Flash Macro Control
Address: 0x4024F000
Offset: 0x0
Retention: Not Retained
IsDeepSleep: No
Comment: The register fields are related to C interface functionality
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			FM_MODE [4:0]				
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	EMB_START [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	FM_MODE	RW	RW	0	Flash macro mode selection: d0: Read/Idle - Normal mode, read array enabled d1: Not Used - the 1st analog POR is done by enable/enable_hv d2 - POR FUR Download - Downloads critical Flash initialization data from OTP (BG, rd, redu, etc....) d3 - POR IRAM MMR Download - Downloads from OTP region the MMR / IRAM into to the 8051 RDL shadows d4 - POR SW Download - Downloads from OTP region the SW code into to the 8051 MCU SRAM d5 - POR Code_Work Prepare - Loads the Code and Work Flash MG's to be ready for user mode operation d6 - Not Used d7 - Program 32b (WORK) - Used as program confirm command for 32 (Work) bits program d8 - Program 64b (CODE) - Used as program confirm command for 64 (Code) bits program d9 - Program 256b (CODE) - Used as program confirm command for 256 (Code) bits program d10: Program Page (CODE) - Used as program confirm command for page program for Code flash d11: Not Used d12 - Sector Erase - Erase for all kinds of sectors (Code/Work/SMS) d13 - Blank check Entry (UBC) d14 - Blank Check Read 32bit (WORK) - Blank check mode d15 - Blank check Exit d16 - Not Used d17 - Erase Suspend - Suspend command to the Erase operation d18 - Erase Resume - Resume command to Erase suspended operation d19 - Not Used d20- Not Used d21- Not Used d22- Not Used d23- Not Used d24- Not Used d25- Not Used d26- Not Used d27- Not Used d28- Not Used d29- Not Used d30: Not Used d31: Not Used
31	EMB_START	RW	RW	0	'0': not active '1': starts the actual embedded operation

14.2.24.2 FLASHC_FM_CODE_MARGIN

Description: Flash Macro Margin Mode on Code Flash
Address: 0x4024F004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment: This register shell be used when Margin read is applied to the s40ect Flash IP. One should set the DCS trim that serves as the reference current to the area between 4-8uA (around the 6uA normal static ref current) and set the enable. After that one should wait ~10uSec before starting to read any data in the Code Flash. Once Finished the MARGIN_MODE_EN should be reset. Again, user should wait ~10uSec before continue to work with the Flash normally.
Default: 0x3943

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MARGIN_DCS_TRIM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MARGIN_RDREG_TRIM [15:10]						MARGIN_DCS_TRIM_EN [9:9]	MARGIN_DCS_TRIM [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MARGIN_MODE_EN [31:31]	MARGIN_MODE_RDREG_CHNG_EN [30:30]	MARGIN_PGM_ERS_B [29:29]	None [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	MARGIN_DCS_TRIM	RW	RW	323	see above table to set the DCS reference current value to be used during Margin mode. (default set to 5uS = 0x143) which gives a Margin to the Erase side. 7uA would probably be used for Margin to the PGM side
9	MARGIN_DCS_TRIM_EN	RW	RW	0	0: internal device defaults used from Margin reads reference current 1: MARGIN_DCS_TRIM configuration is used during Margin read
10:15	MARGIN_RDREG_TRIM	RW	RW	14	rdreg_c trim to be used in Margin mode if enabled by MARGIN_MODE_RDREG_CHNG_EN
29	MARGIN_PGM_ERS_B	RW	RW	0	0: ERS Margin is checked 1: PGM Margin is checked
30	MARGIN_MODE_RDREG_CHNG_EN	RW	RW	0	when set will also use the MARGIN_RDREG_TRIM from above. Default is not to use
31	MARGIN_MODE_EN	RW	RW	0	when set puts the s40ect Flash IP In Margin mode

14.2.24.3 FLASHC_FM_ADDR

Description: Flash Macro Address

Address: 0x4024F008

Offset: 0x8

Retention: Not Retained

IsDeepSleep: No

Comment: This register specifies the flash memory address till the byte resolution. This register defines the address space for both Code and Work Flash and it works according to the address scheme tables defined below (also used as the address definition for R-bus (code_r_addr and work_r_addr))

This FM_ADDR should be used whenever a user mode embedded operation is done on the Flash i.e. PGM/ERS

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FM_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	FM_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	FM_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	FM_ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	FM_ADDR	W	W	0	Code or Work Flash Address to be used during write operations (PGM/ERS)

14.2.24.4 FLASHC_INTR

Description: Interrupt
Address: 0x4024F020
Offset: 0x20
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INTR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INTR	RW1C	RW1C	0	Set to '1', when event is detected. Write INTR field with '1', to clear bit. Write INTR_SET field with '1', to set bit.

14.2.24.5 FLASHC_INTR_SET

Description: Interrupt Set
Address: 0x4024F024
Offset: 0x24
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INTR_SET [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INTR_SET	RW1S	RW1S	0	Write INTR_SET field with '1' to set corresponding INTR field (a write of '0' has no effect).

14.2.24.6 FLASHC_INTR_MASK

Description: Interrupt Mask
Address: 0x4024F028
Offset: 0x28
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INTR_MASK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INTR_MASK	RW	RW	0	Mask for corresponding field in the INTR register

14.2.24.7 FLASHC_INTR_MASKED

Description: Interrupt Masked
Address: 0x4024F02C
Offset: 0x2C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INTR_MASKED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INTR_MASKED	R	R	0	Logical and of corresponding request and mask fields.

14.2.24.8 FLASHC_ECC_OVERRIDE

Description: ECC Data In override information and control bits
Address: 0x4024F030
Offset: 0x30
Retention: Not Retained
IsDeepSleep: No
Comment: The replacement can be either to the Code syndrome or the work flash syndrome. It knows to replace only 8 bits (per 64) in code flash OR 7 bits (per 32) in work flash, therefore this option is valid only for pgm64 command (Code) or pgm32 command (Work)
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ECC_OVERRIDE_SYNDROME [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ECC_OVERRIDE_CODE [31:31]	ECC_OVERRIDE_WORK [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ECC_OVERRIDE_SYNDROME	W	W	0	The override syndrome itself to be used in case one of the enables are set. It will take [7:0] in the case of Code flash and [6:0] in the case of work flash, to bypass the internal generated syndrome
30	ECC_OVERRIDE_WORK	W	W	0	0: no override. Using internal ECC engine to calculate the ECC of the Work Flash
31	ECC_OVERRIDE_CODE	W	W	0	0: no override. Using internal ECC engine to calculate the ECC of the Code Flash

14.2.24.9 FLASHC_FM_DATA

Description: Flash macro data_in[31 to 0] both Code and Work Flash
Address: 0x4024F040
Offset: 0x40
Retention: Not Retained
IsDeepSleep: No
Comment: These registers support aligned 32-bit accesses. The usage of this register should follow the PGM sequence defined (and implemented by API). It has restrictions on the FM_ADDR and # of writes that can be done per pgm command (64,256,page for Code or 32 to work flash) and therefore the sequence must be correct. These register are related to C interface functionality.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FM_DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	FM_DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	FM_DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	FM_DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	FM_DATA	W	W	0	Pgm command data in going to the internal write buffer (WBUF).

14.2.24.10 FLASHC_BOOKMARK

Description: Bookmark register - keeps the current FW HV seq
Address: 0x4024F064
Offset: 0x64
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BOOKMARK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	BOOKMARK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BOOKMARK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BOOKMARK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	BOOKMARK	RW	RW	0	Used by FW. Keeps the Current HV cycle sequence

14.2.24.11 FLASHC_MAIN_FLASH_SAFETY

Description: Main (Code) Flash Security enable
Address: 0x4024F400
Offset: 0x400
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MAINFLASH WRITEENABL E [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MAINFLASH WRITEENABLE	RW	RW	0	'0': Main Flash embedded operations are blocked '1': Main Flash embedded operations are enabled

14.2.24.12 FLASHC_STATUS

Description: Status read from Flash Macro
Address: 0x4024F404
Offset: 0x404
Retention: Not Retained
IsDeepSleep: No
Comment: Read out by the CPUSS to understand the Flash Macro status
Default: 0x80000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	BLANK_CHCEK_PASS [6:6]	BLANK_CHECK_WORK [5:5]	ERS_SUSPEND [4:4]	ERASE_WORK [3:3]	ERASE_CODE [2:2]	PGM_WORK [1:1]	PGM_CODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	HANG [30:30]	NATIVE_POR [29:29]	POR_2B_ECC_ERROR [28:28]	POR_1B_ECC_CORRECTED [27:27]	None [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PGM_CODE	R	R	0	Indicates if active PGM operation to the Code flash is taking place 0: not running 1: running
1	PGM_WORK	R	R	0	Indicates if active PGM operation to the Work flash is taking place 0: not running 1: running
2	ERASE_CODE	R	R	0	Indicates if active Erase operation to the Code flash is taking place 0: not running 1: running
3	ERASE_WORK	R	R	0	Indicates if active Erase operation to the Work flash is taking place 0: not running 1: running
4	ERS_SUSPEND	R	R	0	Indicates if Erase operation (Code/Work) is currently being suspended 0: not suspended 1: suspended
5	BLANK_CHECK_WORK	R	R	0	Indicates if Blank Check mode is currently running on the work flash 0: not running 1: running
6	BLANK_CHCEK_PASS	R	R	0	Indicates the Blank check command result is PASS (Blank) 0: Not Blank 1: Blank (PASS)

Bits	Name	SW	HW	Default or Enum	Description
27	POR_1B_ECC_CORRECTED	R	R	0	Indicates internal ECC found 1b error while downloading info in POR from NVM to VM and fixed it. Valid after 2nd, 3rd and 4th POR phases (FUR, IREM & MMR, SW DOWNLOAD). If Set it is not cleaned till additional POR (rst_hf_ac_t) 0: No error 1: 1b ECC Error corrected in POR
28	POR_2B_ECC_ERROR	R	R	0	Indicates an internal ECC error of 2b while downloading info in POR from NVM to VM. Valid after 2nd, 3rd and 4th POR phases (FUR, IREM & MMR, SW DOWNLOAD). If Set it is not cleaned till additional POR (rst_hf_ac_t) 0: No error 1: ECC 2b Error in POR
29	NATIVE_POR	R	R	0	Indicates a Native Flash state (UV) or sorted one. Valid only after 2nd phase of POR (FUR DOWNLOAD). Comment: not a retained flop, therefore reset (rst_hf_act_n) puts it back to 0. If Set it is not cleaned till additional POR (rst_hf_ac_t) 0: SORTED DEVICE (Non - Native) 1: NATIVE
30	HANG	R	R	0	After embedded operation (pgm/erase) this flag will tell if it was successful or failed 0: PASS 1: FAIL
31	BUSY	R	R	1	Whenever the device is in embedded mode the RDY goes low. Should be the same as c_interrupt pin of the IP (but inverted) 1: busy in embedded 0: rdy (high also in erase suspend)

14.2.24.13 FLASHC_WORK_FLASH_SAFETY

Description: Work Flash Security enable
Address: 0x4024F500
Offset: 0x500
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WORKFLASH WRITEENABL E [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WORKFLASH WRITEENABLE	RW	RW	0	0: Work Flash embedded operations are blocked 1: Work Flash embedded operations are enabled

15 GPIO

Description	GPIO port control/configuration
Base Address	0x40310000
Size	0x10000
Slave Num	MMIO3 - 1

Register Name	Address	Permission	Description
GPIO_INTR_CAUSE0	0x40314000	FULL	Interrupt port cause register 0
GPIO_INTR_CAUSE1	0x40314004	FULL	Interrupt port cause register 1
GPIO_VDD_ACTIVE	0x40314010	FULL	Extern power supply detection register
GPIO_VDD_INTR	0x40314014	FULL	Supply detection interrupt register
GPIO_VDD_INTR_MASK	0x40314018	FULL	Supply detection interrupt mask register
GPIO_VDD_INTR_MASKED	0x4031401C	FULL	Supply detection interrupt masked register
GPIO_VDD_INTR_SET	0x40314020	FULL	Supply detection interrupt set register

15.1 PRT 0

Register Name	Address	Permission	Description
GPIO_PRT0_OUT	0x40310000	FULL	Port output data register Note:OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT0_OUT_CLR	0x40310004	FULL	Port output data clear register
GPIO_PRT0_OUT_SET	0x40310008	FULL	Port output data set register
GPIO_PRT0_OUT_INV	0x4031000C	FULL	Port output data invert register
GPIO_PRT0_IN	0x40310010	FULL	Port input state register Note:IN4 IN5 IN6 IN7 are not available for this register
GPIO_PRT0_INTR	0x40310014	FULL	Port interrupt status register Note:EDGE4 EDGE5 EDGE6 EDGE7 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT0_INTR_MASK	0x40310018	FULL	Port interrupt mask register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT0_INTR_MASKED	0x4031001C	FULL	Port interrupt masked status register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT0_INTR_SET	0x40310020	FULL	Port interrupt set register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT0_INTR_CFG	0x40310040	FULL	Port interrupt configuration register Note:EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT0_CFG	0x40310044	FULL	Port configuration register Note:DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT0_CFG_IN	0x40310048	FULL	Port input buffer configuration register Note:VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT0_CFG_OUT	0x4031004C	FULL	Port output buffer configuration register Note:SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT0_CFG_IN_AUTOLVL	0x40310058	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.2 PRT 1

Register Name	Address	Permission	Description
GPIO_PRT1_OUT	0x40310080	FULL	Port output data register Note:OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT1_OUT_CLR	0x40310084	FULL	Port output data clear register
GPIO_PRT1_OUT_SET	0x40310088	FULL	Port output data set register
GPIO_PRT1_OUT_INV	0x4031008C	FULL	Port output data invert register
GPIO_PRT1_IN	0x40310090	FULL	Port input state register Note:IN5 IN6 IN7 are not available for this register

Register Name	Address	Permission	Description
GPIO_PRT1_INTR	0x40310094	FULL	Port interrupt status register Note:EDGE5 EDGE6 EDGE7 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT1_INTR_MASK	0x40310098	FULL	Port interrupt mask register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT1_INTR_MASKED	0x4031009C	FULL	Port interrupt masked status register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT1_INTR_SET	0x403100A0	FULL	Port interrupt set register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT1_INTR_CFG	0x403100C0	FULL	Port interrupt configuration register Note:EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT1_CFG	0x403100C4	FULL	Port configuration register Note:DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT1_CFG_IN	0x403100C8	FULL	Port input buffer configuration register Note:VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT1_CFG_OUT	0x403100CC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT1_CFG_IN_AUTOLVL	0x403100D8	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.3 PRT 2

Register Name	Address	Permission	Description
GPIO_PRT2_OUT	0x40310100	FULL	Port output data register
GPIO_PRT2_OUT_CLR	0x40310104	FULL	Port output data clear register
GPIO_PRT2_OUT_SET	0x40310108	FULL	Port output data set register
GPIO_PRT2_OUT_INV	0x4031010C	FULL	Port output data invert register
GPIO_PRT2_IN	0x40310110	FULL	Port input state register
GPIO_PRT2_INTR	0x40310114	FULL	Port interrupt status register
GPIO_PRT2_INTR_MASK	0x40310118	FULL	Port interrupt mask register
GPIO_PRT2_INTR_MASKED	0x4031011C	FULL	Port interrupt masked status register
GPIO_PRT2_INTR_SET	0x40310120	FULL	Port interrupt set register
GPIO_PRT2_INTR_CFG	0x40310140	FULL	Port interrupt configuration register
GPIO_PRT2_CFG	0x40310144	FULL	Port configuration register
GPIO_PRT2_CFG_IN	0x40310148	FULL	Port input buffer configuration register
GPIO_PRT2_CFG_OUT	0x4031014C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT2_CFG_IN_AUTOLVL	0x40310158	FULL	Port input buffer AUTOLVL configuration register

15.4 PRT 3

Register Name	Address	Permission	Description
GPIO_PRT3_OUT	0x40310180	FULL	Port output data register
GPIO_PRT3_OUT_CLR	0x40310184	FULL	Port output data clear register
GPIO_PRT3_OUT_SET	0x40310188	FULL	Port output data set register
GPIO_PRT3_OUT_INV	0x4031018C	FULL	Port output data invert register
GPIO_PRT3_IN	0x40310190	FULL	Port input state register
GPIO_PRT3_INTR	0x40310194	FULL	Port interrupt status register
GPIO_PRT3_INTR_MASK	0x40310198	FULL	Port interrupt mask register
GPIO_PRT3_INTR_MASKED	0x4031019C	FULL	Port interrupt masked status register
GPIO_PRT3_INTR_SET	0x403101A0	FULL	Port interrupt set register
GPIO_PRT3_INTR_CFG	0x403101C0	FULL	Port interrupt configuration register
GPIO_PRT3_CFG	0x403101C4	FULL	Port configuration register
GPIO_PRT3_CFG_IN	0x403101C8	FULL	Port input buffer configuration register
GPIO_PRT3_CFG_OUT	0x403101CC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register

Register Name	Address	Permission	Description
GPIO_PRT3_CFG_IN_AUTOLVL	0x403101D8	FULL	Port input buffer AUTOLVL configuration register

15.5 PRT 4

Register Name	Address	Permission	Description
GPIO_PRT4_OUT	0x40310200	FULL	Port output data register Note:OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT4_OUT_CLR	0x40310204	FULL	Port output data clear register
GPIO_PRT4_OUT_SET	0x40310208	FULL	Port output data set register
GPIO_PRT4_OUT_INV	0x4031020C	FULL	Port output data invert register
GPIO_PRT4_IN	0x40310210	FULL	Port input state register Note:IN5 IN6 IN7 are not available for this register
GPIO_PRT4_INTR	0x40310214	FULL	Port interrupt status register Note:EDGE5 EDGE6 EDGE7 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT4_INTR_MASK	0x40310218	FULL	Port interrupt mask register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT4_INTR_MASKED	0x4031021C	FULL	Port interrupt masked status register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT4_INTR_SET	0x40310220	FULL	Port interrupt set register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT4_INTR_CFG	0x40310240	FULL	Port interrupt configuration register Note:EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT4_CFG	0x40310244	FULL	Port configuration register Note:DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT4_CFG_IN	0x40310248	FULL	Port input buffer configuration register Note:VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT4_CFG_OUT	0x4031024C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT4_CFG_IN_AUTOLVL	0x40310258	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.6 PRT 5

Register Name	Address	Permission	Description
GPIO_PRT5_OUT	0x40310280	FULL	Port output data register Note:OUT6 OUT7 are not available for this register
GPIO_PRT5_OUT_CLR	0x40310284	FULL	Port output data clear register
GPIO_PRT5_OUT_SET	0x40310288	FULL	Port output data set register
GPIO_PRT5_OUT_INV	0x4031028C	FULL	Port output data invert register
GPIO_PRT5_IN	0x40310290	FULL	Port input state register Note:IN6 IN7 are not available for this register
GPIO_PRT5_INTR	0x40310294	FULL	Port interrupt status register Note:EDGE6 EDGE7 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT5_INTR_MASK	0x40310298	FULL	Port interrupt mask register Note:EDGE6 EDGE7 are not available for this register
GPIO_PRT5_INTR_MASKED	0x4031029C	FULL	Port interrupt masked status register Note:EDGE6 EDGE7 are not available for this register
GPIO_PRT5_INTR_SET	0x403102A0	FULL	Port interrupt set register Note:EDGE6 EDGE7 are not available for this register
GPIO_PRT5_INTR_CFG	0x403102C0	FULL	Port interrupt configuration register Note:EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT5_CFG	0x403102C4	FULL	Port configuration register Note:DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register

Register Name	Address	Permission	Description
GPIO_PRT5_CFG_IN	0x403102C8	FULL	Port input buffer configuration register Note: VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT5_CFG_OUT	0x403102CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT5_CFG_IN_AUTOLVL	0x403102D8	FULL	Port input buffer AUTOLVL configuration register Note: VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.7 PRT 6

Register Name	Address	Permission	Description
GPIO_PRT6_OUT	0x40310300	FULL	Port output data register
GPIO_PRT6_OUT_CLR	0x40310304	FULL	Port output data clear register
GPIO_PRT6_OUT_SET	0x40310308	FULL	Port output data set register
GPIO_PRT6_OUT_INV	0x4031030C	FULL	Port output data invert register
GPIO_PRT6_IN	0x40310310	FULL	Port input state register
GPIO_PRT6_INTR	0x40310314	FULL	Port interrupt status register
GPIO_PRT6_INTR_MASK	0x40310318	FULL	Port interrupt mask register
GPIO_PRT6_INTR_MASKED	0x4031031C	FULL	Port interrupt masked status register
GPIO_PRT6_INTR_SET	0x40310320	FULL	Port interrupt set register
GPIO_PRT6_INTR_CFG	0x40310340	FULL	Port interrupt configuration register
GPIO_PRT6_CFG	0x40310344	FULL	Port configuration register
GPIO_PRT6_CFG_IN	0x40310348	FULL	Port input buffer configuration register
GPIO_PRT6_CFG_OUT	0x4031034C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT6_CFG_IN_AUTOLVL	0x40310358	FULL	Port input buffer AUTOLVL configuration register

15.8 PRT 7

Register Name	Address	Permission	Description
GPIO_PRT7_OUT	0x40310380	FULL	Port output data register
GPIO_PRT7_OUT_CLR	0x40310384	FULL	Port output data clear register
GPIO_PRT7_OUT_SET	0x40310388	FULL	Port output data set register
GPIO_PRT7_OUT_INV	0x4031038C	FULL	Port output data invert register
GPIO_PRT7_IN	0x40310390	FULL	Port input state register
GPIO_PRT7_INTR	0x40310394	FULL	Port interrupt status register
GPIO_PRT7_INTR_MASK	0x40310398	FULL	Port interrupt mask register
GPIO_PRT7_INTR_MASKED	0x4031039C	FULL	Port interrupt masked status register
GPIO_PRT7_INTR_SET	0x403103A0	FULL	Port interrupt set register
GPIO_PRT7_INTR_CFG	0x403103C0	FULL	Port interrupt configuration register
GPIO_PRT7_CFG	0x403103C4	FULL	Port configuration register
GPIO_PRT7_CFG_IN	0x403103C8	FULL	Port input buffer configuration register
GPIO_PRT7_CFG_OUT	0x403103CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT7_CFG_IN_AUTOLVL	0x403103D8	FULL	Port input buffer AUTOLVL configuration register

15.9 PRT 8

Register Name	Address	Permission	Description
GPIO_PRT8_OUT	0x40310400	FULL	Port output data register Note: OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT8_OUT_CLR	0x40310404	FULL	Port output data clear register
GPIO_PRT8_OUT_SET	0x40310408	FULL	Port output data set register
GPIO_PRT8_OUT_INV	0x4031040C	FULL	Port output data invert register
GPIO_PRT8_IN	0x40310410	FULL	Port input state register Note: IN5 IN6 IN7 are not available for this register
GPIO_PRT8_INTR	0x40310414	FULL	Port interrupt status register Note: EDGE5 EDGE6 EDGE7 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT8_INTR_MASK	0x40310418	FULL	Port interrupt mask register Note: EDGE5 EDGE6 EDGE7 are not available for this register

Register Name	Address	Permission	Description
GPIO_PRT8_INTR_MASKED	0x4031041C	FULL	Port interrupt masked status register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT8_INTR_SET	0x40310420	FULL	Port interrupt set register Note:EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT8_INTR_CFG	0x40310440	FULL	Port interrupt configuration register Note:EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT8_CFG	0x40310444	FULL	Port configuration register Note:DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT8_CFG_IN	0x40310448	FULL	Port input buffer configuration register Note:VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT8_CFG_OUT	0x4031044C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT8_CFG_IN_AUTOLVL	0x40310458	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.10 PRT 9

Register Name	Address	Permission	Description
GPIO_PRT9_OUT	0x40310480	FULL	Port output data register Note:OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT9_OUT_CLR	0x40310484	FULL	Port output data clear register
GPIO_PRT9_OUT_SET	0x40310488	FULL	Port output data set register
GPIO_PRT9_OUT_INV	0x4031048C	FULL	Port output data invert register
GPIO_PRT9_IN	0x40310490	FULL	Port input state register Note:IN4 IN5 IN6 IN7 are not available for this register
GPIO_PRT9_INTR	0x40310494	FULL	Port interrupt status register Note:EDGE4 EDGE5 EDGE6 EDGE7 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT9_INTR_MASK	0x40310498	FULL	Port interrupt mask register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT9_INTR_MASKED	0x4031049C	FULL	Port interrupt masked status register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT9_INTR_SET	0x403104A0	FULL	Port interrupt set register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT9_INTR_CFG	0x403104C0	FULL	Port interrupt configuration register Note:EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT9_CFG	0x403104C4	FULL	Port configuration register Note:DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT9_CFG_IN	0x403104C8	FULL	Port input buffer configuration register Note:VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT9_CFG_OUT	0x403104CC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT9_CFG_IN_AUTOLVL	0x403104D8	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.11 PRT 10

Register Name	Address	Permission	Description
GPIO_PRT10_OUT	0x40310500	FULL	Port output data register

Register Name	Address	Permission	Description
GPIO_PRT10_OUT_CLR	0x40310504	FULL	Port output data clear register
GPIO_PRT10_OUT_SET	0x40310508	FULL	Port output data set register
GPIO_PRT10_OUT_INV	0x4031050C	FULL	Port output data invert register
GPIO_PRT10_IN	0x40310510	FULL	Port input state register
GPIO_PRT10_INTR	0x40310514	FULL	Port interrupt status register
GPIO_PRT10_INTR_MASK	0x40310518	FULL	Port interrupt mask register
GPIO_PRT10_INTR_MASKED	0x4031051C	FULL	Port interrupt masked status register
GPIO_PRT10_INTR_SET	0x40310520	FULL	Port interrupt set register
GPIO_PRT10_INTR_CFG	0x40310540	FULL	Port interrupt configuration register
GPIO_PRT10_CFG	0x40310544	FULL	Port configuration register
GPIO_PRT10_CFG_IN	0x40310548	FULL	Port input buffer configuration register
GPIO_PRT10_CFG_OUT	0x4031054C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT10_CFG_IN_AUTOLVL	0x40310558	FULL	Port input buffer AUTOLVL configuration register

15.12 PRT 11

Register Name	Address	Permission	Description
GPIO_PRT11_OUT	0x40310580	FULL	Port output data register Note: OUT3 OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT11_OUT_CLR	0x40310584	FULL	Port output data clear register
GPIO_PRT11_OUT_SET	0x40310588	FULL	Port output data set register
GPIO_PRT11_OUT_INV	0x4031058C	FULL	Port output data invert register
GPIO_PRT11_IN	0x40310590	FULL	Port input state register Note: IN3 IN4 IN5 IN6 IN7 are not available for this register
GPIO_PRT11_INTR	0x40310594	FULL	Port interrupt status register Note: EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 IN_IN3 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT11_INTR_MASK	0x40310598	FULL	Port interrupt mask register Note: EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT11_INTR_MASKED	0x4031059C	FULL	Port interrupt masked status register Note: EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT11_INTR_SET	0x403105A0	FULL	Port interrupt set register Note: EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT11_INTR_CFG	0x403105C0	FULL	Port interrupt configuration register Note: EDGE3_SEL EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT11_CFG	0x403105C4	FULL	Port configuration register Note: DRIVE_MODE3 IN_EN3 DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT11_CFG_IN	0x403105C8	FULL	Port input buffer configuration register Note: VTRIP_SEL3_0 VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT11_CFG_OUT	0x403105CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL3 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT11_CFG_IN_AUTOLVL	0x403105D8	FULL	Port input buffer AUTOLVL configuration register Note: VTRIP_SEL3_1 VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.13 PRT 12

Register Name	Address	Permission	Description
GPIO_PRT12_OUT	0x40310600	FULL	Port output data register
GPIO_PRT12_OUT_CLR	0x40310604	FULL	Port output data clear register

Register Name	Address	Permission	Description
GPIO_PRT12_OUT_SET	0x40310608	FULL	Port output data set register
GPIO_PRT12_OUT_INV	0x4031060C	FULL	Port output data invert register
GPIO_PRT12_IN	0x40310610	FULL	Port input state register
GPIO_PRT12_INTR	0x40310614	FULL	Port interrupt status register
GPIO_PRT12_INTR_MASK	0x40310618	FULL	Port interrupt mask register
GPIO_PRT12_INTR_MASKED	0x4031061C	FULL	Port interrupt masked status register
GPIO_PRT12_INTR_SET	0x40310620	FULL	Port interrupt set register
GPIO_PRT12_INTR_CFG	0x40310640	FULL	Port interrupt configuration register
GPIO_PRT12_CFG	0x40310644	FULL	Port configuration register
GPIO_PRT12_CFG_IN	0x40310648	FULL	Port input buffer configuration register
GPIO_PRT12_CFG_OUT	0x4031064C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT12_CFG_IN_AUTOLVL	0x40310658	FULL	Port input buffer AUTOLVL configuration register

15.14 PRT 13

Register Name	Address	Permission	Description
GPIO_PRT13_OUT	0x40310680	FULL	Port output data register
GPIO_PRT13_OUT_CLR	0x40310684	FULL	Port output data clear register
GPIO_PRT13_OUT_SET	0x40310688	FULL	Port output data set register
GPIO_PRT13_OUT_INV	0x4031068C	FULL	Port output data invert register
GPIO_PRT13_IN	0x40310690	FULL	Port input state register
GPIO_PRT13_INTR	0x40310694	FULL	Port interrupt status register
GPIO_PRT13_INTR_MASK	0x40310698	FULL	Port interrupt mask register
GPIO_PRT13_INTR_MASKED	0x4031069C	FULL	Port interrupt masked status register
GPIO_PRT13_INTR_SET	0x403106A0	FULL	Port interrupt set register
GPIO_PRT13_INTR_CFG	0x403106C0	FULL	Port interrupt configuration register
GPIO_PRT13_CFG	0x403106C4	FULL	Port configuration register
GPIO_PRT13_CFG_IN	0x403106C8	FULL	Port input buffer configuration register
GPIO_PRT13_CFG_OUT	0x403106CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT13_CFG_IN_AUTOLVL	0x403106D8	FULL	Port input buffer AUTOLVL configuration register

15.15 PRT 14

Register Name	Address	Permission	Description
GPIO_PRT14_OUT	0x40310700	FULL	Port output data register
GPIO_PRT14_OUT_CLR	0x40310704	FULL	Port output data clear register
GPIO_PRT14_OUT_SET	0x40310708	FULL	Port output data set register
GPIO_PRT14_OUT_INV	0x4031070C	FULL	Port output data invert register
GPIO_PRT14_IN	0x40310710	FULL	Port input state register
GPIO_PRT14_INTR	0x40310714	FULL	Port interrupt status register
GPIO_PRT14_INTR_MASK	0x40310718	FULL	Port interrupt mask register
GPIO_PRT14_INTR_MASKED	0x4031071C	FULL	Port interrupt masked status register
GPIO_PRT14_INTR_SET	0x40310720	FULL	Port interrupt set register
GPIO_PRT14_INTR_CFG	0x40310740	FULL	Port interrupt configuration register
GPIO_PRT14_CFG	0x40310744	FULL	Port configuration register
GPIO_PRT14_CFG_IN	0x40310748	FULL	Port input buffer configuration register
GPIO_PRT14_CFG_OUT	0x4031074C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT14_CFG_IN_AUTOLVL	0x40310758	FULL	Port input buffer AUTOLVL configuration register

15.16 PRT 15

Register Name	Address	Permission	Description
GPIO_PRT15_OUT	0x40310780	FULL	Port output data register Note: OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT15_OUT_CLR	0x40310784	FULL	Port output data clear register
GPIO_PRT15_OUT_SET	0x40310788	FULL	Port output data set register
GPIO_PRT15_OUT_INV	0x4031078C	FULL	Port output data invert register
GPIO_PRT15_IN	0x40310790	FULL	Port input state register Note: IN4 IN5 IN6 IN7 are not available for this register

Register Name	Address	Permission	Description
GPIO_PRT15_INTR	0x40310794	FULL	Port interrupt status register Note:EDGE4 EDGE5 EDGE6 EDGE7 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT15_INTR_MASK	0x40310798	FULL	Port interrupt mask register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT15_INTR_MASKED	0x4031079C	FULL	Port interrupt masked status register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT15_INTR_SET	0x403107A0	FULL	Port interrupt set register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT15_INTR_CFG	0x403107C0	FULL	Port interrupt configuration register Note:EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT15_CFG	0x403107C4	FULL	Port configuration register Note:DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT15_CFG_IN	0x403107C8	FULL	Port input buffer configuration register Note:VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT15_CFG_OUT	0x403107CC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT15_CFG_IN_AUTOLVL	0x403107D8	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.17 PRT 16

Register Name	Address	Permission	Description
GPIO_PRT16_OUT	0x40310800	FULL	Port output data register
GPIO_PRT16_OUT_CLR	0x40310804	FULL	Port output data clear register
GPIO_PRT16_OUT_SET	0x40310808	FULL	Port output data set register
GPIO_PRT16_OUT_INV	0x4031080C	FULL	Port output data invert register
GPIO_PRT16_IN	0x40310810	FULL	Port input state register
GPIO_PRT16_INTR	0x40310814	FULL	Port interrupt status register
GPIO_PRT16_INTR_MASK	0x40310818	FULL	Port interrupt mask register
GPIO_PRT16_INTR_MASKED	0x4031081C	FULL	Port interrupt masked status register
GPIO_PRT16_INTR_SET	0x40310820	FULL	Port interrupt set register
GPIO_PRT16_INTR_CFG	0x40310840	FULL	Port interrupt configuration register
GPIO_PRT16_CFG	0x40310844	FULL	Port configuration register
GPIO_PRT16_CFG_IN	0x40310848	FULL	Port input buffer configuration register
GPIO_PRT16_CFG_OUT	0x4031084C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT16_CFG_IN_AUTOLVL	0x40310858	FULL	Port input buffer AUTOLVL configuration register

15.18 PRT 17

Register Name	Address	Permission	Description
GPIO_PRT17_OUT	0x40310880	FULL	Port output data register
GPIO_PRT17_OUT_CLR	0x40310884	FULL	Port output data clear register
GPIO_PRT17_OUT_SET	0x40310888	FULL	Port output data set register
GPIO_PRT17_OUT_INV	0x4031088C	FULL	Port output data invert register
GPIO_PRT17_IN	0x40310890	FULL	Port input state register
GPIO_PRT17_INTR	0x40310894	FULL	Port interrupt status register
GPIO_PRT17_INTR_MASK	0x40310898	FULL	Port interrupt mask register
GPIO_PRT17_INTR_MASKED	0x4031089C	FULL	Port interrupt masked status register
GPIO_PRT17_INTR_SET	0x403108A0	FULL	Port interrupt set register
GPIO_PRT17_INTR_CFG	0x403108C0	FULL	Port interrupt configuration register
GPIO_PRT17_CFG	0x403108C4	FULL	Port configuration register
GPIO_PRT17_CFG_IN	0x403108C8	FULL	Port input buffer configuration register

Register Name	Address	Permission	Description
GPIO_PRT17_CFG_OUT	0x403108CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT17_CFG_IN_AUTOLVL	0x403108D8	FULL	Port input buffer AUTOLVL configuration register

15.19 PRT 18

Register Name	Address	Permission	Description
GPIO_PRT18_OUT	0x40310900	FULL	Port output data register
GPIO_PRT18_OUT_CLR	0x40310904	FULL	Port output data clear register
GPIO_PRT18_OUT_SET	0x40310908	FULL	Port output data set register
GPIO_PRT18_OUT_INV	0x4031090C	FULL	Port output data invert register
GPIO_PRT18_IN	0x40310910	FULL	Port input state register
GPIO_PRT18_INTR	0x40310914	FULL	Port interrupt status register
GPIO_PRT18_INTR_MASK	0x40310918	FULL	Port interrupt mask register
GPIO_PRT18_INTR_MASKED	0x4031091C	FULL	Port interrupt masked status register
GPIO_PRT18_INTR_SET	0x40310920	FULL	Port interrupt set register
GPIO_PRT18_INTR_CFG	0x40310940	FULL	Port interrupt configuration register
GPIO_PRT18_CFG	0x40310944	FULL	Port configuration register
GPIO_PRT18_CFG_IN	0x40310948	FULL	Port input buffer configuration register
GPIO_PRT18_CFG_OUT	0x4031094C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT18_CFG_IN_AUTOLVL	0x40310958	FULL	Port input buffer AUTOLVL configuration register

15.20 PRT 19

Register Name	Address	Permission	Description
GPIO_PRT19_OUT	0x40310980	FULL	Port output data register Note: OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT19_OUT_CLR	0x40310984	FULL	Port output data clear register
GPIO_PRT19_OUT_SET	0x40310988	FULL	Port output data set register
GPIO_PRT19_OUT_INV	0x4031098C	FULL	Port output data invert register
GPIO_PRT19_IN	0x40310990	FULL	Port input state register Note: IN5 IN6 IN7 are not available for this register
GPIO_PRT19_INTR	0x40310994	FULL	Port interrupt status register Note: EDGE5 EDGE6 EDGE7 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT19_INTR_MASK	0x40310998	FULL	Port interrupt mask register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT19_INTR_MASKED	0x4031099C	FULL	Port interrupt masked status register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT19_INTR_SET	0x403109A0	FULL	Port interrupt set register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT19_INTR_CFG	0x403109C0	FULL	Port interrupt configuration register Note: EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT19_CFG	0x403109C4	FULL	Port configuration register Note: DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT19_CFG_IN	0x403109C8	FULL	Port input buffer configuration register Note: VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT19_CFG_OUT	0x403109CC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT19_CFG_IN_AUTOLVL	0x403109D8	FULL	Port input buffer AUTOLVL configuration register Note: VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.21 PRT 20

Register Name	Address	Permission	Description
GPIO_PRT20_OUT	0x40310A00	FULL	Port output data register

Register Name	Address	Permission	Description
GPIO_PRT20_OUT_CLR	0x40310A04	FULL	Port output data clear register
GPIO_PRT20_OUT_SET	0x40310A08	FULL	Port output data set register
GPIO_PRT20_OUT_INV	0x40310A0C	FULL	Port output data invert register
GPIO_PRT20_IN	0x40310A10	FULL	Port input state register
GPIO_PRT20_INTR	0x40310A14	FULL	Port interrupt status register
GPIO_PRT20_INTR_MASK	0x40310A18	FULL	Port interrupt mask register
GPIO_PRT20_INTR_MASKED	0x40310A1C	FULL	Port interrupt masked status register
GPIO_PRT20_INTR_SET	0x40310A20	FULL	Port interrupt set register
GPIO_PRT20_INTR_CFG	0x40310A40	FULL	Port interrupt configuration register
GPIO_PRT20_CFG	0x40310A44	FULL	Port configuration register
GPIO_PRT20_CFG_IN	0x40310A48	FULL	Port input buffer configuration register
GPIO_PRT20_CFG_OUT	0x40310A4C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT20_CFG_IN_AUTOLVL	0x40310A58	FULL	Port input buffer AUTOLVL configuration register

15.22 PRT 21

Register Name	Address	Permission	Description
GPIO_PRT21_OUT	0x40310A80	FULL	Port output data register
GPIO_PRT21_OUT_CLR	0x40310A84	FULL	Port output data clear register
GPIO_PRT21_OUT_SET	0x40310A88	FULL	Port output data set register
GPIO_PRT21_OUT_INV	0x40310A8C	FULL	Port output data invert register
GPIO_PRT21_IN	0x40310A90	FULL	Port input state register
GPIO_PRT21_INTR	0x40310A94	FULL	Port interrupt status register
GPIO_PRT21_INTR_MASK	0x40310A98	FULL	Port interrupt mask register
GPIO_PRT21_INTR_MASKED	0x40310A9C	FULL	Port interrupt masked status register
GPIO_PRT21_INTR_SET	0x40310AA0	FULL	Port interrupt set register
GPIO_PRT21_INTR_CFG	0x40310AC0	FULL	Port interrupt configuration register
GPIO_PRT21_CFG	0x40310AC4	FULL	Port configuration register
GPIO_PRT21_CFG_IN	0x40310AC8	FULL	Port input buffer configuration register
GPIO_PRT21_CFG_OUT	0x40310ACC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT21_CFG_IN_AUTOLVL	0x40310AD8	FULL	Port input buffer AUTOLVL configuration register

15.23 PRT 22

Register Name	Address	Permission	Description
GPIO_PRT22_OUT	0x40310B00	FULL	Port output data register
GPIO_PRT22_OUT_CLR	0x40310B04	FULL	Port output data clear register
GPIO_PRT22_OUT_SET	0x40310B08	FULL	Port output data set register
GPIO_PRT22_OUT_INV	0x40310B0C	FULL	Port output data invert register
GPIO_PRT22_IN	0x40310B10	FULL	Port input state register
GPIO_PRT22_INTR	0x40310B14	FULL	Port interrupt status register
GPIO_PRT22_INTR_MASK	0x40310B18	FULL	Port interrupt mask register
GPIO_PRT22_INTR_MASKED	0x40310B1C	FULL	Port interrupt masked status register
GPIO_PRT22_INTR_SET	0x40310B20	FULL	Port interrupt set register
GPIO_PRT22_INTR_CFG	0x40310B40	FULL	Port interrupt configuration register
GPIO_PRT22_CFG	0x40310B44	FULL	Port configuration register
GPIO_PRT22_CFG_IN	0x40310B48	FULL	Port input buffer configuration register
GPIO_PRT22_CFG_OUT	0x40310B4C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT22_CFG_IN_AUTOLVL	0x40310B58	FULL	Port input buffer AUTOLVL configuration register

15.24 PRT 23

Register Name	Address	Permission	Description
GPIO_PRT23_OUT	0x40310B80	FULL	Port output data register
GPIO_PRT23_OUT_CLR	0x40310B84	FULL	Port output data clear register
GPIO_PRT23_OUT_SET	0x40310B88	FULL	Port output data set register
GPIO_PRT23_OUT_INV	0x40310B8C	FULL	Port output data invert register
GPIO_PRT23_IN	0x40310B90	FULL	Port input state register
GPIO_PRT23_INTR	0x40310B94	FULL	Port interrupt status register

Register Name	Address	Permission	Description
GPIO_PRT23_INTR_MASK	0x40310B98	FULL	Port interrupt mask register
GPIO_PRT23_INTR_MASKED	0x40310B9C	FULL	Port interrupt masked status register
GPIO_PRT23_INTR_SET	0x40310BA0	FULL	Port interrupt set register
GPIO_PRT23_INTR_CFG	0x40310BC0	FULL	Port interrupt configuration register
GPIO_PRT23_CFG	0x40310BC4	FULL	Port configuration register
GPIO_PRT23_CFG_IN	0x40310BC8	FULL	Port input buffer configuration register
GPIO_PRT23_CFG_OUT	0x40310BCC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT23_CFG_IN_AUTOLVL	0x40310BD8	FULL	Port input buffer AUTOLVL configuration register

15.25 PRT 24

Register Name	Address	Permission	Description
GPIO_PRT24_OUT	0x40310C00	FULL	Port output data register Note: OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT24_OUT_CLR	0x40310C04	FULL	Port output data clear register
GPIO_PRT24_OUT_SET	0x40310C08	FULL	Port output data set register
GPIO_PRT24_OUT_INV	0x40310C0C	FULL	Port output data invert register
GPIO_PRT24_IN	0x40310C10	FULL	Port input state register Note: IN5 IN6 IN7 are not available for this register
GPIO_PRT24_INTR	0x40310C14	FULL	Port interrupt status register Note: EDGE5 EDGE6 EDGE7 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT24_INTR_MASK	0x40310C18	FULL	Port interrupt mask register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT24_INTR_MASKED	0x40310C1C	FULL	Port interrupt masked status register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT24_INTR_SET	0x40310C20	FULL	Port interrupt set register Note: EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT24_INTR_CFG	0x40310C40	FULL	Port interrupt configuration register Note: EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT24_CFG	0x40310C44	FULL	Port configuration register Note: DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT24_CFG_IN	0x40310C48	FULL	Port input buffer configuration register Note: VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT24_CFG_OUT	0x40310C4C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT24_CFG_IN_AUTOLVL	0x40310C58	FULL	Port input buffer AUTOLVL configuration register Note: VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.26 PRT 25

Register Name	Address	Permission	Description
GPIO_PRT25_OUT	0x40310C80	FULL	Port output data register
GPIO_PRT25_OUT_CLR	0x40310C84	FULL	Port output data clear register
GPIO_PRT25_OUT_SET	0x40310C88	FULL	Port output data set register
GPIO_PRT25_OUT_INV	0x40310C8C	FULL	Port output data invert register
GPIO_PRT25_IN	0x40310C90	FULL	Port input state register
GPIO_PRT25_INTR	0x40310C94	FULL	Port interrupt status register
GPIO_PRT25_INTR_MASK	0x40310C98	FULL	Port interrupt mask register
GPIO_PRT25_INTR_MASKED	0x40310C9C	FULL	Port interrupt masked status register
GPIO_PRT25_INTR_SET	0x40310CA0	FULL	Port interrupt set register
GPIO_PRT25_INTR_CFG	0x40310CC0	FULL	Port interrupt configuration register
GPIO_PRT25_CFG	0x40310CC4	FULL	Port configuration register
GPIO_PRT25_CFG_IN	0x40310CC8	FULL	Port input buffer configuration register

Register Name	Address	Permission	Description
GPIO_PRT25_CFG_OUT	0x40310CCC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT25_CFG_IN_AUTOLVL	0x40310CD8	FULL	Port input buffer AUTOLVL configuration register

15.27 PRT 26

Register Name	Address	Permission	Description
GPIO_PRT26_OUT	0x40310D00	FULL	Port output data register
GPIO_PRT26_OUT_CLR	0x40310D04	FULL	Port output data clear register
GPIO_PRT26_OUT_SET	0x40310D08	FULL	Port output data set register
GPIO_PRT26_OUT_INV	0x40310D0C	FULL	Port output data invert register
GPIO_PRT26_IN	0x40310D10	FULL	Port input state register
GPIO_PRT26_INTR	0x40310D14	FULL	Port interrupt status register
GPIO_PRT26_INTR_MASK	0x40310D18	FULL	Port interrupt mask register
GPIO_PRT26_INTR_MASKED	0x40310D1C	FULL	Port interrupt masked status register
GPIO_PRT26_INTR_SET	0x40310D20	FULL	Port interrupt set register
GPIO_PRT26_INTR_CFG	0x40310D40	FULL	Port interrupt configuration register
GPIO_PRT26_CFG	0x40310D44	FULL	Port configuration register
GPIO_PRT26_CFG_IN	0x40310D48	FULL	Port input buffer configuration register
GPIO_PRT26_CFG_OUT	0x40310D4C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT26_CFG_IN_AUTOLVL	0x40310D58	FULL	Port input buffer AUTOLVL configuration register

15.28 PRT 27

Register Name	Address	Permission	Description
GPIO_PRT27_OUT	0x40310D80	FULL	Port output data register
GPIO_PRT27_OUT_CLR	0x40310D84	FULL	Port output data clear register
GPIO_PRT27_OUT_SET	0x40310D88	FULL	Port output data set register
GPIO_PRT27_OUT_INV	0x40310D8C	FULL	Port output data invert register
GPIO_PRT27_IN	0x40310D90	FULL	Port input state register
GPIO_PRT27_INTR	0x40310D94	FULL	Port interrupt status register
GPIO_PRT27_INTR_MASK	0x40310D98	FULL	Port interrupt mask register
GPIO_PRT27_INTR_MASKED	0x40310D9C	FULL	Port interrupt masked status register
GPIO_PRT27_INTR_SET	0x40310DA0	FULL	Port interrupt set register
GPIO_PRT27_INTR_CFG	0x40310DC0	FULL	Port interrupt configuration register
GPIO_PRT27_CFG	0x40310DC4	FULL	Port configuration register
GPIO_PRT27_CFG_IN	0x40310DC8	FULL	Port input buffer configuration register
GPIO_PRT27_CFG_OUT	0x40310DCC	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT27_CFG_IN_AUTOLVL	0x40310DD8	FULL	Port input buffer AUTOLVL configuration register

15.29 PRT 28

Register Name	Address	Permission	Description
GPIO_PRT28_OUT	0x40310E00	FULL	Port output data register
GPIO_PRT28_OUT_CLR	0x40310E04	FULL	Port output data clear register
GPIO_PRT28_OUT_SET	0x40310E08	FULL	Port output data set register
GPIO_PRT28_OUT_INV	0x40310E0C	FULL	Port output data invert register
GPIO_PRT28_IN	0x40310E10	FULL	Port input state register
GPIO_PRT28_INTR	0x40310E14	FULL	Port interrupt status register
GPIO_PRT28_INTR_MASK	0x40310E18	FULL	Port interrupt mask register
GPIO_PRT28_INTR_MASKED	0x40310E1C	FULL	Port interrupt masked status register
GPIO_PRT28_INTR_SET	0x40310E20	FULL	Port interrupt set register
GPIO_PRT28_INTR_CFG	0x40310E40	FULL	Port interrupt configuration register
GPIO_PRT28_CFG	0x40310E44	FULL	Port configuration register
GPIO_PRT28_CFG_IN	0x40310E48	FULL	Port input buffer configuration register
GPIO_PRT28_CFG_OUT	0x40310E4C	FULL	Port output buffer configuration register Note: SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT28_CFG_IN_AUTOLVL	0x40310E58	FULL	Port input buffer AUTOLVL configuration register

15.30 PRT 29

Register Name	Address	Permission	Description
GPIO_PRT29_OUT	0x40310E80	FULL	Port output data register
GPIO_PRT29_OUT_CLR	0x40310E84	FULL	Port output data clear register
GPIO_PRT29_OUT_SET	0x40310E88	FULL	Port output data set register
GPIO_PRT29_OUT_INV	0x40310E8C	FULL	Port output data invert register
GPIO_PRT29_IN	0x40310E90	FULL	Port input state register
GPIO_PRT29_INTR	0x40310E94	FULL	Port interrupt status register
GPIO_PRT29_INTR_MASK	0x40310E98	FULL	Port interrupt mask register
GPIO_PRT29_INTR_MASKED	0x40310E9C	FULL	Port interrupt masked status register
GPIO_PRT29_INTR_SET	0x40310EA0	FULL	Port interrupt set register
GPIO_PRT29_INTR_CFG	0x40310EC0	FULL	Port interrupt configuration register
GPIO_PRT29_CFG	0x40310EC4	FULL	Port configuration register
GPIO_PRT29_CFG_IN	0x40310EC8	FULL	Port input buffer configuration register
GPIO_PRT29_CFG_OUT	0x40310ECC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT29_CFG_IN_AUTOLVL	0x40310ED8	FULL	Port input buffer AUTOLVL configuration register

15.31 PRT 30

Register Name	Address	Permission	Description
GPIO_PRT30_OUT	0x40310F00	FULL	Port output data register Note:OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT30_OUT_CLR	0x40310F04	FULL	Port output data clear register
GPIO_PRT30_OUT_SET	0x40310F08	FULL	Port output data set register
GPIO_PRT30_OUT_INV	0x40310F0C	FULL	Port output data invert register
GPIO_PRT30_IN	0x40310F10	FULL	Port input state register Note:IN4 IN5 IN6 IN7 are not available for this register
GPIO_PRT30_INTR	0x40310F14	FULL	Port interrupt status register Note:EDGE4 EDGE5 EDGE6 EDGE7 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT30_INTR_MASK	0x40310F18	FULL	Port interrupt mask register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT30_INTR_MASKED	0x40310F1C	FULL	Port interrupt masked status register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT30_INTR_SET	0x40310F20	FULL	Port interrupt set register Note:EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT30_INTR_CFG	0x40310F40	FULL	Port interrupt configuration register Note:EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT30_CFG	0x40310F44	FULL	Port configuration register Note:DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT30_CFG_IN	0x40310F48	FULL	Port input buffer configuration register Note:VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT30_CFG_OUT	0x40310F4C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT30_CFG_IN_AUTOLVL	0x40310F58	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.32 PRT 31

Register Name	Address	Permission	Description
GPIO_PRT31_OUT	0x40310F80	FULL	Port output data register Note:OUT3 OUT4 OUT5 OUT6 OUT7 are not available for this register
GPIO_PRT31_OUT_CLR	0x40310F84	FULL	Port output data clear register
GPIO_PRT31_OUT_SET	0x40310F88	FULL	Port output data set register
GPIO_PRT31_OUT_INV	0x40310F8C	FULL	Port output data invert register

Register Name	Address	Permission	Description
GPIO_PRT31_IN	0x40310F90	FULL	Port input state register Note:IN3 IN4 IN5 IN6 IN7 are not available for this register
GPIO_PRT31_INTR	0x40310F94	FULL	Port interrupt status register Note:EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 IN_IN3 IN_IN4 IN_IN5 IN_IN6 IN_IN7 are not available for this register
GPIO_PRT31_INTR_MASK	0x40310F98	FULL	Port interrupt mask register Note:EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT31_INTR_MASKED	0x40310F9C	FULL	Port interrupt masked status register Note:EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT31_INTR_SET	0x40310FA0	FULL	Port interrupt set register Note:EDGE3 EDGE4 EDGE5 EDGE6 EDGE7 are not available for this register
GPIO_PRT31_INTR_CFG	0x40310FC0	FULL	Port interrupt configuration register Note:EDGE3_SEL EDGE4_SEL EDGE5_SEL EDGE6_SEL EDGE7_SEL are not available for this register
GPIO_PRT31_CFG	0x40310FC4	FULL	Port configuration register Note:DRIVE_MODE3 IN_EN3 DRIVE_MODE4 IN_EN4 DRIVE_MODE5 IN_EN5 DRIVE_MODE6 IN_EN6 DRIVE_MODE7 IN_EN7 are not available for this register
GPIO_PRT31_CFG_IN	0x40310FC8	FULL	Port input buffer configuration register Note:VTRIP_SEL3_0 VTRIP_SEL4_0 VTRIP_SEL5_0 VTRIP_SEL6_0 VTRIP_SEL7_0 are not available for this register
GPIO_PRT31_CFG_OUT	0x40310FCC	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 DRIVE_SEL3 DRIVE_SEL4 DRIVE_SEL5 DRIVE_SEL6 DRIVE_SEL7 are not available for this register
GPIO_PRT31_CFG_IN_AUTOLVL	0x40310FD8	FULL	Port input buffer AUTOLVL configuration register Note:VTRIP_SEL3_1 VTRIP_SEL4_1 VTRIP_SEL5_1 VTRIP_SEL6_1 VTRIP_SEL7_1 are not available for this register

15.33 PRT 32

Register Name	Address	Permission	Description
GPIO_PRT32_OUT	0x40311000	FULL	Port output data register
GPIO_PRT32_OUT_CLR	0x40311004	FULL	Port output data clear register
GPIO_PRT32_OUT_SET	0x40311008	FULL	Port output data set register
GPIO_PRT32_OUT_INV	0x4031100C	FULL	Port output data invert register
GPIO_PRT32_IN	0x40311010	FULL	Port input state register
GPIO_PRT32_INTR	0x40311014	FULL	Port interrupt status register
GPIO_PRT32_INTR_MASK	0x40311018	FULL	Port interrupt mask register
GPIO_PRT32_INTR_MASKED	0x4031101C	FULL	Port interrupt masked status register
GPIO_PRT32_INTR_SET	0x40311020	FULL	Port interrupt set register
GPIO_PRT32_INTR_CFG	0x40311040	FULL	Port interrupt configuration register
GPIO_PRT32_CFG	0x40311044	FULL	Port configuration register
GPIO_PRT32_CFG_IN	0x40311048	FULL	Port input buffer configuration register
GPIO_PRT32_CFG_OUT	0x4031104C	FULL	Port output buffer configuration register Note:SLOW0 SLOW1 SLOW2 SLOW3 SLOW4 SLOW5 SLOW6 SLOW7 are not available for this register
GPIO_PRT32_CFG_IN_AUTOLVL	0x40311058	FULL	Port input buffer AUTOLVL configuration register

15.34 Register Details

15.34.1 GPIO_INTR_CAUSE0

Description: Interrupt port cause register 0
Address: 0x40314000
Offset: 0x4000
Retention: Retained
IsDeepSleep: No
Comment: This register provides interrupt status corresponding to ports 0 to 31
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PORT_INT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	PORT_INT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	PORT_INT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	PORT_INT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	PORT_INT	R	R	0	Each IO port has an associated bit field in this register. The bit field reflects the IO port's interrupt line (bit field <i>i</i> reflects 'gpio_interrupts[i]' for IO port <i>i</i>). The register is used when the system uses a combined interrupt line 'gpio_interrupt'. The software ISR reads the register to determine which IO port(s) is responsible for the combined interrupt line. Once, the IO port(s) is determined, the IO port's GPIO_PRT_INTR register is read to determine the IO pin(s) in the IO port that caused the interrupt. '0': Port has no pending interrupt '1': Port has pending interrupt

15.34.2 GPIO_INTR_CAUSE1

Description: Interrupt port cause register 1
Address: 0x40314004
Offset: 0x4004
Retention: Retained
IsDeepSleep: No
Comment: This register provides interrupt status corresponding to ports 32 to 63
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PORT_INT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PORT_INT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PORT_INT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PORT_INT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	PORT_INT	R	R	0	Each IO port has an associated bit field in this register. The bit field reflects the IO port's interrupt line (bit field i reflects 'gpio_interrupts[i]' for IO port i). The register is used when the system uses a combined interrupt line 'gpio_interrupt'. The software ISR reads the register to determine which IO port(s) is responsible for the combined interrupt line. Once, the IO port(s) is determined, the IO port's GPIO_PORT_INTR register is read to determine the IO pin(s) in the IO port that caused the interrupt. '0': Port has no pending interrupt '1': Port has pending interrupt

15.34.3 GPIO_VDD_ACTIVE

Description: Extern power supply detection register
Address: 0x40314010
Offset: 0x4010
Retention: Retained
IsDeepSleep: No
Comment: This register provides external power supply status
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VDDIO_ACTIVE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VDDIO_ACTIVE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VDDD_ACTIVE [31:31]	VDDA_ACTIVE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VDDIO_ACTIVE	R	R	0	Indicates presence or absence of VDDIO supplies (i.e. other than VDDD, VDDA) on the device (supplies are numbered 0..n-1). Note that VDDIO supplies have basic (crude) supply detectors only. If separate, robust, brown-out detection is desired on IO supplies, on-chip or off-chip analog resources need to provide it. For these bits to work reliable, the supply must be within valid spec range (per datasheet) or held at ground. Any in-between voltage has an undefined result. '0': Supply is not present '1': Supply is present When multiple VDDIO supplies are present, they will be assigned in alphanumeric ascending order to these bits during implementation. For example 'vddusb, vddio_0, vddio_a, vbackup, vddio_r, vddio_1' are present then they will be assigned to these bits as below: 0: vbackup, 1: vddio_0, 2: vddio_1, 3: vddio_a, 4: vddio_r, 5: vddusb'
30	VDDA_ACTIVE	R	R	0	Same as VDDIO_ACTIVE for the analog supply VDDA.
31	VDDD_ACTIVE	R	R	0	This bit indicates presence of the VDDD supply. This bit will always read-back 1. The VDDD supply has robust brown-out protection monitoring and it is not possible to read back this register without a valid supply. (This bit is used in certain test-modes to observe the brown-out detector status.)

15.34.4 GPIO_VDD_INTR

Description: Supply detection interrupt register

Address: 0x40314014

Offset: 0x4014

Retention: Retained

IsDeepSleep: No

Comment: An interrupt cause is cleared (set to '0') by writing a '1' to the corresponding bit field. It is not recommended to write 0xFF to clear all interrupt causes, as a new interrupt cause may have occurred between reading the register and clearing. Note that the interrupt cause fields and the associated interrupt provide DeepSleep functionality (interrupt causes can be set to '1' and cause the system to wake up from DeepSleep power mode). This register is set whenever a supply ramp up or ramp down is detected. Some bits may be set after system power-up, depending on power supply sequencing.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VDDIO_ACTIVE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VDDIO_ACTIVE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VDDD_ACTIVE [31:31]	VDDA_ACTIVE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VDDIO_ACTIVE	RW1C	RW1C	0	Supply state change detected. '0': No change to supply detected '1': Change to supply detected
30	VDDA_ACTIVE	RW1C	RW1C	0	Same as VDDIO_ACTIVE for the analog supply VDDA.
31	VDDD_ACTIVE	RW1C	RW1C	0	The VDDD supply is always present during operation so a supply transition can not occur. This bit will always read back '1'.

15.34.5 GPIO_VDD_INTR_MASK

Description: Supply detection interrupt mask register
Address: 0x40314018
Offset: 0x4018
Retention: Retained
IsDeepSleep: No
Comment: This register configures the supply detection interrupts for all supplies. This register only masks the forwarding of interrupts to the CPU(s), it does not enable/disable the logging of interrupts into the VDD_INTR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VDDIO_ACTIVE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VDDIO_ACTIVE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VDDD_ACTIVE [31:31]	VDDA_ACTIVE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VDDIO_ACTIVE	RW	RW	0	Masks supply interrupt on VDDIO. '0': VDDIO interrupt forwarding disabled '1': VDDIO interrupt forwarding enabled
30	VDDA_ACTIVE	RW	RW	0	Same as VDDIO_ACTIVE for the analog supply VDDA.
31	VDDD_ACTIVE	RW	RW	0	Same as VDDIO_ACTIVE for the digital supply VDDD.

15.34.6 GPIO_VDD_INTR_MASKED

Description: Supply detection interrupt masked register
Address: 0x4031401C
Offset: 0x401C
Retention: Retained
IsDeepSleep: No
Comment: This register contains the AND-ed values of VDD_INTR and VDD_INTR_MASK registers
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VDDIO_ACTIVE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VDDIO_ACTIVE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VDDD_ACTIVE [31:31]	VDDA_ACTIVE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VDDIO_ACTIVE	R	R	0	Supply transition detected AND masked '0': Interrupt was not forwarded to CPU '1': Interrupt occurred and was forwarded to CPU
30	VDDA_ACTIVE	R	R	0	Same as VDDIO_ACTIVE for the analog supply VDDA.
31	VDDD_ACTIVE	R	R	0	Same as VDDIO_ACTIVE for the digital supply VDDD.

15.34.7 GPIO_VDD_INTR_SET

Description: Supply detection interrupt set register
Address: 0x40314020
Offset: 0x4020
Retention: Retained
IsDeepSleep: No
Comment: Allows firmware or debugger to set interrupt bits in the VDD_INTR register by writing a '1' to the corresponding bit field. When read, returns the same value as the VDD_INTR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VDDIO_ACTIVE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	VDDIO_ACTIVE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VDDD_ACTIVE [31:31]	VDDA_ACTIVE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	VDDIO_ACTIVE	RW1S	RW1S	0	Sets supply interrupt. '0': Interrupt state not affected '1': Interrupt set
30	VDDA_ACTIVE	RW1S	RW1S	0	Same as VDDIO_ACTIVE for the analog supply VDDA.
31	VDDD_ACTIVE	RW1S	RW1S	0	Same as VDDIO_ACTIVE for the digital supply VDDD.

15.34.8 PRT

15.34.8.1 GPIO_PRT_OUT

Description:	Port output data register
Address:	0x40310000
Offset:	0x0
Retention:	Retained
IsDeepSleep:	No
Comment:	Used to read and write the output data for the IO pins in the port. A register write changes the output data to the written value. A register read reflects the output data (and not the current state of the input data for the IO pins). Using this register, Read-Modify-Write sequences are safely performed on a port with some IO pins configured as inputs.
Default:	0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUT7 [7:7]	OUT6 [6:6]	OUT5 [5:5]	OUT4 [4:4]	OUT3 [3:3]	OUT2 [2:2]	OUT1 [1:1]	OUT0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	OUT0	RW	RW	0	IO output data for pin 0 '0': Output state set to '0' '1': Output state set to '1'
1	OUT1	RW	RW	0	IO output data for pin 1
2	OUT2	RW	RW	0	IO output data for pin 2
3	OUT3	RW	RW	0	IO output data for pin 3
4	OUT4	RW	RW	0	IO output data for pin 4
5	OUT5	RW	RW	0	IO output data for pin 5
6	OUT6	RW	RW	0	IO output data for pin 6
7	OUT7	RW	RW	0	IO output data for pin 7

15.34.8.2 GPIO_PRT_OUT_CLR

Description: Port output data clear register

Address: 0x40310004

Offset: 0x4

Retention: Retained

IsDeepSleep: No

Comment: Used to clear output data of specific IO pins in the corresponding port to '0', without affecting the output data of the other IO pads in the port. A register read returns the same value as an OUT register read.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUT7 [7:7]	OUT6 [6:6]	OUT5 [5:5]	OUT4 [4:4]	OUT3 [3:3]	OUT2 [2:2]	OUT1 [1:1]	OUT0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	OUT0	RW	RW	0	IO clear output for pin 0: '0': Output state not affected. '1': Output state set to '0'.
1	OUT1	RW	RW	0	IO clear output for pin 1
2	OUT2	RW	RW	0	IO clear output for pin 2
3	OUT3	RW	RW	0	IO clear output for pin 3
4	OUT4	RW	RW	0	IO clear output for pin 4
5	OUT5	RW	RW	0	IO clear output for pin 5
6	OUT6	RW	RW	0	IO clear output for pin 6
7	OUT7	RW	RW	0	IO clear output for pin 7

15.34.8.3 GPIO_PRT_OUT_SET

Description: Port output data set register

Address: 0x40310008

Offset: 0x8

Retention: Retained

IsDeepSleep: No

Comment: Used to set output data of specific IO pins in the corresponding port to '1', without affecting the output data of the other IO pads in the port. A register read returns the same value as an OUT register read.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUT7 [7:7]	OUT6 [6:6]	OUT5 [5:5]	OUT4 [4:4]	OUT3 [3:3]	OUT2 [2:2]	OUT1 [1:1]	OUT0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	OUT0	RW	RW	0	IO set output for pin 0: '0': Output state not affected. '1': Output state set to '1'.
1	OUT1	RW	RW	0	IO set output for pin 1
2	OUT2	RW	RW	0	IO set output for pin 2
3	OUT3	RW	RW	0	IO set output for pin 3
4	OUT4	RW	RW	0	IO set output for pin 4
5	OUT5	RW	RW	0	IO set output for pin 5
6	OUT6	RW	RW	0	IO set output for pin 6
7	OUT7	RW	RW	0	IO set output for pin 7

15.34.8.4 GPIO_PRT_OUT_INV

Description: Port output data invert register
Address: 0x4031000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Used to invert output data of specific IO pins in the corresponding port, without affecting the output data of the other IO pads in the port. A register read returns the same value as an OUT register read.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUT7 [7:7]	OUT6 [6:6]	OUT5 [5:5]	OUT4 [4:4]	OUT3 [3:3]	OUT2 [2:2]	OUT1 [1:1]	OUT0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	OUT0	RW	RW	0	IO invert output for pin 0: '0': Output state not affected. '1': Output state inverted ('0' => '1', '1' => '0').
1	OUT1	RW	RW	0	IO invert output for pin 1
2	OUT2	RW	RW	0	IO invert output for pin 2
3	OUT3	RW	RW	0	IO invert output for pin 3
4	OUT4	RW	RW	0	IO invert output for pin 4
5	OUT5	RW	RW	0	IO invert output for pin 5
6	OUT6	RW	RW	0	IO invert output for pin 6
7	OUT7	RW	RW	0	IO invert output for pin 7

15.34.8.5 GPIO_PRT_IN

Description: Port input state register
Address: 0x40310010
Offset: 0x10
Retention: Not Retained
IsDeepSleep: No
Comment: Used to read current pin status for IO pins that have their input buffer enabled (see CFG_IN).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IN7 [7:7]	IN6 [6:6]	IN5 [5:5]	IN4 [4:4]	IN3 [3:3]	IN2 [2:2]	IN1 [1:1]	IN0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							FLT_IN [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	IN0	R	R	0	IO pin state for pin 0 '0': Low logic level present on pin. '1': High logic level present on pin. On reset assertion , IN register will get reset. The Pad value takes 2 clock cycles to be reflected into IN Register. It's value then depends on the external pin value.
1	IN1	R	R	0	IO pin state for pin 1
2	IN2	R	R	0	IO pin state for pin 2
3	IN3	R	R	0	IO pin state for pin 3
4	IN4	R	R	0	IO pin state for pin 4
5	IN5	R	R	0	IO pin state for pin 5
6	IN6	R	R	0	IO pin state for pin 6
7	IN7	R	R	0	IO pin state for pin 7
8	FLT_IN	R	R	0	Reads of this register return the logical state of the filtered pin as selected in the INTR_CFG.FLT_SEL register.

15.34.8.6 GPIO_PRT_INTR

Description: Port interrupt status register

Address: 0x40310014

Offset: 0x14

Retention: Retained

IsDeepSleep: No

Comment: An interrupt cause is cleared (set to '0') by writing a '1' to the corresponding bit field. It is not recommended to write 0xFF to clear all interrupt causes, as a new interrupt cause may have occurred between reading the register and clearing. Note that the pin interrupt provide DeepSleep functionality (interrupt causes can be set to '1' and cause the system to wake up from DeepSleep power mode). The IN.IN fields reflect the logical IO pin states at the time of reading this register (same as the IN register).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EDGE7 [7:7]	EDGE6 [6:6]	EDGE5 [5:5]	EDGE4 [4:4]	EDGE3 [3:3]	EDGE2 [2:2]	EDGE1 [1:1]	EDGE0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							FLT_EDGE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	IN_IN7 [23:23]	IN_IN6 [22:22]	IN_IN5 [21:21]	IN_IN4 [20:20]	IN_IN3 [19:19]	IN_IN2 [18:18]	IN_IN1 [17:17]	IN_IN0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							FLT_IN_IN [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EDGE0	RW1C	RW1C	0	Edge detect for IO pin 0 '0': No edge was detected on pin. '1': An edge was detected on pin.
1	EDGE1	RW1C	RW1C	0	Edge detect for IO pin 1
2	EDGE2	RW1C	RW1C	0	Edge detect for IO pin 2
3	EDGE3	RW1C	RW1C	0	Edge detect for IO pin 3
4	EDGE4	RW1C	RW1C	0	Edge detect for IO pin 4
5	EDGE5	RW1C	RW1C	0	Edge detect for IO pin 5
6	EDGE6	RW1C	RW1C	0	Edge detect for IO pin 6
7	EDGE7	RW1C	RW1C	0	Edge detect for IO pin 7
8	FLT_EDGE	RW1C	RW1C	0	Edge detected on filtered pin selected by INTR_CFG.FLT_SEL
16	IN_IN0	R	R	0	IO pin state for pin 0
17	IN_IN1	R	R	0	IO pin state for pin 1
18	IN_IN2	R	R	0	IO pin state for pin 2
19	IN_IN3	R	R	0	IO pin state for pin 3
20	IN_IN4	R	R	0	IO pin state for pin 4
21	IN_IN5	R	R	0	IO pin state for pin 5
22	IN_IN6	R	R	0	IO pin state for pin 6
23	IN_IN7	R	R	0	IO pin state for pin 7
24	FLT_IN_IN	R	R	0	Filtered pin state for pin selected by INTR_CFG.FLT_SEL

15.34.8.7 GPIO_PRT_INTR_MASK

Description: Port interrupt mask register

Address: 0x40310018

Offset: 0x18

Retention: Retained

IsDeepSleep: No

Comment: This register configures the edge detection interrupts for all pins in a port. This register only masks the forwarding of interrupts to the CPU(s) interrupt controller, it does not enable/disable the logging of interrupts into the INTR register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EDGE7 [7:7]	EDGE6 [6:6]	EDGE5 [5:5]	EDGE4 [4:4]	EDGE3 [3:3]	EDGE2 [2:2]	EDGE1 [1:1]	EDGE0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							FLT_EDGE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EDGE0	RW	RW	0	Masks edge interrupt on IO pin 0 '0': Pin interrupt forwarding disabled '1': Pin interrupt forwarding enabled
1	EDGE1	RW	RW	0	Masks edge interrupt on IO pin 1
2	EDGE2	RW	RW	0	Masks edge interrupt on IO pin 2
3	EDGE3	RW	RW	0	Masks edge interrupt on IO pin 3
4	EDGE4	RW	RW	0	Masks edge interrupt on IO pin 4
5	EDGE5	RW	RW	0	Masks edge interrupt on IO pin 5
6	EDGE6	RW	RW	0	Masks edge interrupt on IO pin 6
7	EDGE7	RW	RW	0	Masks edge interrupt on IO pin 7
8	FLT_EDGE	RW	RW	0	Masks edge interrupt on filtered pin selected by INTR_CFG.FLT_SEL

15.34.8.8 GPIO_PRT_INTR_MASKED

Description: Port interrupt masked status register
Address: 0x4031001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment: This register contains the AND-ed values of INTR and INTR_MASK registers forwarded to the CPU interrupt controller.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EDGE7 [7:7]	EDGE6 [6:6]	EDGE5 [5:5]	EDGE4 [4:4]	EDGE3 [3:3]	EDGE2 [2:2]	EDGE1 [1:1]	EDGE0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							FLT_EDGE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EDGE0	R	R	0	Edge detected AND masked on IO pin 0 '0': Interrupt was not forwarded to CPU '1': Interrupt occurred and was forwarded to CPU
1	EDGE1	R	R	0	Edge detected and masked on IO pin 1
2	EDGE2	R	R	0	Edge detected and masked on IO pin 2
3	EDGE3	R	R	0	Edge detected and masked on IO pin 3
4	EDGE4	R	R	0	Edge detected and masked on IO pin 4
5	EDGE5	R	R	0	Edge detected and masked on IO pin 5
6	EDGE6	R	R	0	Edge detected and masked on IO pin 6
7	EDGE7	R	R	0	Edge detected and masked on IO pin 7
8	FLT_EDGE	R	R	0	Edge detected and masked on filtered pin selected by INTR_CFG.FLT_SEL

15.34.8.9 GPIO_PRT_INTR_SET

Description: Port interrupt set register
Address: 0x40310020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: Allows firmware or debugger to set interrupt bits in the INTR register by writing a '1' to the corresponding bit field. When read, returns the same value as the INTR register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EDGE7 [7:7]	EDGE6 [6:6]	EDGE5 [5:5]	EDGE4 [4:4]	EDGE3 [3:3]	EDGE2 [2:2]	EDGE1 [1:1]	EDGE0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							FLT_EDGE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EDGE0	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 0 '0': Interrupt state not affected '1': Interrupt set
1	EDGE1	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 1
2	EDGE2	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 2
3	EDGE3	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 3
4	EDGE4	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 4
5	EDGE5	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 5
6	EDGE6	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 6
7	EDGE7	RW1S	RW1S	0	Sets edge detect interrupt for IO pin 7
8	FLT_EDGE	RW1S	RW1S	0	Sets edge detect interrupt for filtered pin selected by INTR_CFG.FLT_SEL

15.34.8.10 GPIO_PRT_INTR_CFG

Description: Port interrupt configuration register
Address: 0x40310040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: This register selects the edge detection type for each pin interrupt.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EDGE3_SEL [7:6]		EDGE2_SEL [5:4]		EDGE1_SEL [3:2]		EDGE0_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	EDGE7_SEL [15:14]		EDGE6_SEL [13:12]		EDGE5_SEL [11:10]		EDGE4_SEL [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			FLT_SEL [20:18]			FLT_EDGE_SEL [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	EDGE0_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 0
	DISABLE			0	Disabled
	RISING			1	Rising edge
	FALLING			2	Falling edge
	BOTH			3	Both rising and falling edges
2:3	EDGE1_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 1
4:5	EDGE2_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 2
6:7	EDGE3_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 3
8:9	EDGE4_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 4
10:11	EDGE5_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 5
12:13	EDGE6_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 6
14:15	EDGE7_SEL	RW	RW	0	Sets which edge will trigger an IRQ for IO pin 7
16:17	FLT_EDGE_SEL	RW	RW	0	Sets which edge will trigger an IRQ for the glitch filtered pin (selected by INTR_CFG.FLT_SEL)
	DISABLE			0	Disabled
	RISING			1	Rising edge
	FALLING			2	Falling edge
	BOTH			3	Both rising and falling edges
18:20	FLT_SEL	RW	RW	0	Selects which pin is routed through the 50ns glitch filter to provide a glitch-safe interrupt.

15.34.8.11 GPIO_PRT_CFG

Description: Port configuration register
Address: 0x40310044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: Configuration of drive mode and input buffer enable for each pin.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IN_EN1 [7:7]	DRIVE_MODE1 [6:4]			IN_EN0 [3:3]	DRIVE_MODE0 [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	IN_EN3 [15:15]	DRIVE_MODE3 [14:12]			IN_EN2 [11:11]	DRIVE_MODE2 [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	IN_EN5 [23:23]	DRIVE_MODE5 [22:20]			IN_EN4 [19:19]	DRIVE_MODE4 [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	IN_EN7 [31:31]	DRIVE_MODE7 [30:28]			IN_EN6 [27:27]	DRIVE_MODE6 [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	DRIVE_MODE0	RW	RW	0	The GPIO drive mode for IO pin 0. Resistive pull-up and pull-down is selected in the drive mode. Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the peripheral and HSIOM (HSIOM_PRT_SELx) is properly configured before turning the IO on here to avoid producing glitches on the bus. Note: that peripherals other than GPIO & UDB/DSI directly control both the output and output-enable of the output buffer (peripherals can drive strong 0 or strong 1 in any mode except OFF='0'). Note: D_OUT, D_OUT_EN are pins of GPIO cell.
	HIGHZ			0	Output buffer is off creating a high impedance input D_OUT = '0': High Impedance D_OUT = '1': High Impedance
	RESERVED			1	N/A

Bits	Name	SW	HW	Default or Enum	Description
	PULLUP			2	Resistive pull up For GPIO & UDB/DSI peripherals: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Weak/resistive pull up When D_OUT_EN = 0: D_OUT = '0': High impedance D_OUT = '1': High impedance For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': Weak/resistive pull up D_OUT = '1': Weak/resistive pull up
	PULLDOWN			3	Resistive pull down For GPIO & UDB/DSI peripherals: When D_OUT_EN = 1: D_OUT = '0': Weak/resistive pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High impedance D_OUT = '1': High impedance For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': Weak/resistive pull down D_OUT = '1': Weak/resistive pull down
	OD_DRIVESLOW			4	Open drain, drives low For GPIO & UDB/DSI peripherals: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': High Impedance When D_OUT_EN = 0: D_OUT = '0': High impedance D_OUT = '1': High impedance For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High Impedance D_OUT = '1': High Impedance

Bits	Name	SW	HW	Default or Enum	Description
	OD_DRIVESHIGH			5	Open drain, drives high For GPIO & UDB/DSI peripherals: When D_OUT_EN = 1: D_OUT = '0': High Impedance D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High impedance D_OUT = '1': High impedance For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High Impedance D_OUT = '1': High Impedance
	STRONG			6	Strong D_OUTput buffer For GPIO & UDB/DSI peripherals: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High impedance D_OUT = '1': High impedance For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': High Impedance D_OUT = '1': High Impedance
	PULLUP_DOWN			7	Pull up or pull down For GPIO & UDB/DSI peripherals: When D_OUT_EN = '0': GPIO_DSI_OUT = '0': Weak/resistive pull down GPIO_DSI_OUT = '1': Weak/resistive pull up where 'GPIO_DSI_OUT' is a function of PORT_SEL, OUT & DSI_DATA_OUT. For peripherals other than GPIO & UDB/DSI: When D_OUT_EN = 1: D_OUT = '0': Strong pull down D_OUT = '1': Strong pull up When D_OUT_EN = 0: D_OUT = '0': Weak/resistive pull down D_OUT = '1': Weak/resistive pull up
3	IN_EN0	RW	RW	0	Enables the input buffer for IO pin 0. This bit should be cleared when analog signals are present on the pin to avoid crowbar currents. The output buffer can be used to drive analog signals high or low without issue. '0': Input buffer disabled '1': Input buffer enabled
4:6	DRIVE_MODE1	RW	RW	0	The GPIO drive mode for IO pin 1
7	IN_EN1	RW	RW	0	Enables the input buffer for IO pin 1
8:10	DRIVE_MODE2	RW	RW	0	The GPIO drive mode for IO pin 2
11	IN_EN2	RW	RW	0	Enables the input buffer for IO pin 2
12:14	DRIVE_MODE3	RW	RW	0	The GPIO drive mode for IO pin 3

Bits	Name	SW	HW	Default or Enum	Description
15	IN_EN3	RW	RW	0	Enables the input buffer for IO pin 3
16:18	DRIVE_MODE4	RW	RW	0	The GPIO drive mode for IO pin4
19	IN_EN4	RW	RW	0	Enables the input buffer for IO pin 4
20:22	DRIVE_MODE5	RW	RW	0	The GPIO drive mode for IO pin 5
23	IN_EN5	RW	RW	0	Enables the input buffer for IO pin 5
24:26	DRIVE_MODE6	RW	RW	0	The GPIO drive mode for IO pin 6
27	IN_EN6	RW	RW	0	Enables the input buffer for IO pin 6
28:30	DRIVE_MODE7	RW	RW	0	The GPIO drive mode for IO pin 7
31	IN_EN7	RW	RW	0	Enables the input buffer for IO pin 7

15.34.8.12 GPIO_PRT_CFG_IN

Description: Port input buffer configuration register
Address: 0x40310048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: Configures the input buffer for each pin and this register is common for PSoC6: & Traveo II: GPIO pins. For Traveo II: GPIO pin, this register control the lower bit i.e. VTRIP_SEL[0].
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VTRIP_SEL_7_0 [7:7]	VTRIP_SEL_6_0 [6:6]	VTRIP_SEL_5_0 [5:5]	VTRIP_SEL_4_0 [4:4]	VTRIP_SEL_3_0 [3:3]	VTRIP_SEL_2_0 [2:2]	VTRIP_SEL_1_0 [1:1]	VTRIP_SEL_0_0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	VTRIP_SEL0_0	RW	RW	0	Configures the pin 0 input buffer mode (trip points and hysteresis)
	CMOS			0	PSoC6:: Input buffer compatible with CMOS and I2C interfaces Traveo II: full encoding is shown in CFG_IN_AUTOLVL.VTRIP_SEL0_1
	TTL			1	PSoC6:: Input buffer compatible with TTL and MediaLB interfaces Traveo II: full encoding is shown in CFG_IN_AUTOLVL.VTRIP_SEL0_1
1	VTRIP_SEL1_0	RW	RW	0	Configures the pin 1 input buffer mode (trip points and hysteresis)
2	VTRIP_SEL2_0	RW	RW	0	Configures the pin 2 input buffer mode (trip points and hysteresis)
3	VTRIP_SEL3_0	RW	RW	0	Configures the pin 3 input buffer mode (trip points and hysteresis)
4	VTRIP_SEL4_0	RW	RW	0	Configures the pin 4 input buffer mode (trip points and hysteresis)
5	VTRIP_SEL5_0	RW	RW	0	Configures the pin 5 input buffer mode (trip points and hysteresis)
6	VTRIP_SEL6_0	RW	RW	0	Configures the pin 6 input buffer mode (trip points and hysteresis)
7	VTRIP_SEL7_0	RW	RW	0	Configures the pin 7 input buffer mode (trip points and hysteresis)

15.34.8.13 GPIO_PRT_CFG_OUT

Description: Port output buffer configuration register

Address: 0x4031004C

Offset: 0x4C

Retention: Retained

IsDeepSleep: No

Comment: Configures the output driver for each pin.

Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the peripheral and HSIOM (HSIOM_PRT_SELx) is properly configured before setting the IO drive mode to avoid producing glitches on the bus.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SLOW7 [7:7]	SLOW6 [6:6]	SLOW5 [5:5]	SLOW4 [4:4]	SLOW3 [3:3]	SLOW2 [2:2]	SLOW1 [1:1]	SLOW0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DRIVE_SEL3 [23:22]		DRIVE_SEL2 [21:20]		DRIVE_SEL1 [19:18]		DRIVE_SEL0 [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	DRIVE_SEL7 [31:30]		DRIVE_SEL6 [29:28]		DRIVE_SEL5 [27:26]		DRIVE_SEL4 [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SLOW0	RW	RW	0	Enables slow slew rate for IO pin 0 '0': Fast slew rate '1': Slow slew rate
1	SLOW1	RW	RW	0	Enables slow slew rate for IO pin 1
2	SLOW2	RW	RW	0	Enables slow slew rate for IO pin 2
3	SLOW3	RW	RW	0	Enables slow slew rate for IO pin 3
4	SLOW4	RW	RW	0	Enables slow slew rate for IO pin 4
5	SLOW5	RW	RW	0	Enables slow slew rate for IO pin 5
6	SLOW6	RW	RW	0	Enables slow slew rate for IO pin 6
7	SLOW7	RW	RW	0	Enables slow slew rate for IO pin 7
16:17	DRIVE_SEL0	RW	RW	0	Sets the GPIO drive strength for IO pin 0
	DRIVE_SEL_ZERO			0	N/A
	DRIVE_SEL_ONE			1	N/A
	DRIVE_SEL_TWO			2	N/A
	DRIVE_SEL_THREE			3	N/A
18:19	DRIVE_SEL1	RW	RW	0	Sets the GPIO drive strength for IO pin 1
20:21	DRIVE_SEL2	RW	RW	0	Sets the GPIO drive strength for IO pin 2
22:23	DRIVE_SEL3	RW	RW	0	Sets the GPIO drive strength for IO pin 3
24:25	DRIVE_SEL4	RW	RW	0	Sets the GPIO drive strength for IO pin 4
26:27	DRIVE_SEL5	RW	RW	0	Sets the GPIO drive strength for IO pin 5
28:29	DRIVE_SEL6	RW	RW	0	Sets the GPIO drive strength for IO pin 6
30:31	DRIVE_SEL7	RW	RW	0	Sets the GPIO drive strength for IO pin 7

15.34.8.14 GPIO_PRT_CFG_IN_AUTOLVL

Description: Port input buffer AUTOLVL configuration register
Address: 0x40310058
Offset: 0x58
Retention: Retained
IsDeepSleep: No
Comment: Configures the GPIO input buffer upper bit i.e. VTRIP_SEL[1] for each pin.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VTRIP_SEL 7_1 [7:7]	VTRIP_SEL 6_1 [6:6]	VTRIP_SEL 5_1 [5:5]	VTRIP_SEL 4_1 [4:4]	VTRIP_SEL 3_1 [3:3]	VTRIP_SEL 2_1 [2:2]	VTRIP_SEL 1_1 [1:1]	VTRIP_SEL 0_1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	VTRIP_SEL0_1	RW	RW	0	Configures the input buffer mode (trip points and hysteresis) for GPIO upper bit. Lower bit is still selected by CFG_IN.VTRIP_SEL0_0 field. This field is used along with CFG_IN.VTRIP_SEL0_0 field as below: {CFG_IN_AUTOLVL.VTRIP_SEL0_1,CFG_IN.VTRIP_SEL0_0}: 0,0: CMOS 0,1: TTL 1,0: input buffer is compatible with automotive. 1,1: input buffer is compatible with automotive.
	CMOS_OR_TTL			0	Input buffer compatible with CMOS/TTL interfaces as described in CFG_IN.VTRIP_SEL0_0.
	AUTO			1	Input buffer compatible with AUTO (elevated Vil) interfaces when used along with CFG_IN.VTRIP_SEL0_0.
1	VTRIP_SEL1_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
2	VTRIP_SEL2_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
3	VTRIP_SEL3_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
4	VTRIP_SEL4_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
5	VTRIP_SEL5_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
6	VTRIP_SEL6_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.
7	VTRIP_SEL7_1	RW	RW	0	Input buffer compatible with automotive (elevated Vil) interfaces.

16 HSIOM

Description	High Speed IO Matrix (HSIOM)
Base Address	0x40300000
Size	0x4000
Slave Num	MMIO3 - 0

Register Name	Address	Permission	Description
HSIOM_AMUX_SPLIT_CTL0	0x40302000	FULL	AMUX splitter cell control
HSIOM_AMUX_SPLIT_CTL1	0x40302004	FULL	AMUX splitter cell control
HSIOM_AMUX_SPLIT_CTL2	0x40302008	FULL	AMUX splitter cell control
HSIOM_MONITOR_CTL_0	0x40302200	FULL	Power/Ground Monitor cell control 0
HSIOM_ALT_JTAG_EN	0x40302240	FULL	Alternate JTAG IF selection register

16.1 PRT 0

Register Name	Address	Permission	Description
HSIOM_PRT0_PORT_SEL0	0x40300000	FULL	Port selection 0

16.2 PRT 1

Register Name	Address	Permission	Description
HSIOM_PRT1_PORT_SEL0	0x40300010	FULL	Port selection 0
HSIOM_PRT1_PORT_SEL1	0x40300014	FULL	Port selection 1 Note: IO5_SEL IO6_SEL IO7_SEL are not available for this register

16.3 PRT 2

Register Name	Address	Permission	Description
HSIOM_PRT2_PORT_SEL0	0x40300020	FULL	Port selection 0
HSIOM_PRT2_PORT_SEL1	0x40300024	FULL	Port selection 1

16.4 PRT 3

Register Name	Address	Permission	Description
HSIOM_PRT3_PORT_SEL0	0x40300030	FULL	Port selection 0
HSIOM_PRT3_PORT_SEL1	0x40300034	FULL	Port selection 1

16.5 PRT 4

Register Name	Address	Permission	Description
HSIOM_PRT4_PORT_SEL0	0x40300040	FULL	Port selection 0
HSIOM_PRT4_PORT_SEL1	0x40300044	FULL	Port selection 1 Note: IO5_SEL IO6_SEL IO7_SEL are not available for this register

16.6 PRT 5

Register Name	Address	Permission	Description
HSIOM_PRT5_PORT_SEL0	0x40300050	FULL	Port selection 0
HSIOM_PRT5_PORT_SEL1	0x40300054	FULL	Port selection 1 Note: IO6_SEL IO7_SEL are not available for this register

16.7 PRT 6

Register Name	Address	Permission	Description
HSIOM_PRT6_PORT_SEL0	0x40300060	FULL	Port selection 0
HSIOM_PRT6_PORT_SEL1	0x40300064	FULL	Port selection 1

16.8 PRT 7

Register Name	Address	Permission	Description
HSIOM_PRT7_PORT_SEL0	0x40300070	FULL	Port selection 0
HSIOM_PRT7_PORT_SEL1	0x40300074	FULL	Port selection 1

16.9 PRT 8

Register Name	Address	Permission	Description
HSIOM_PRT8_PORT_SEL0	0x40300080	FULL	Port selection 0
HSIOM_PRT8_PORT_SEL1	0x40300084	FULL	Port selection 1 <i>Note:IO5_SEL IO6_SEL IO7_SEL are not available for this register</i>

16.10 PRT 9

Register Name	Address	Permission	Description
HSIOM_PRT9_PORT_SEL0	0x40300090	FULL	Port selection 0

16.11 PRT 10

Register Name	Address	Permission	Description
HSIOM_PRT10_PORT_SEL0	0x403000A0	FULL	Port selection 0
HSIOM_PRT10_PORT_SEL1	0x403000A4	FULL	Port selection 1

16.12 PRT 11

Register Name	Address	Permission	Description
HSIOM_PRT11_PORT_SEL0	0x403000B0	FULL	Port selection 0 <i>Note:IO3_SEL is not available for this register</i>

16.13 PRT 12

Register Name	Address	Permission	Description
HSIOM_PRT12_PORT_SEL0	0x403000C0	FULL	Port selection 0
HSIOM_PRT12_PORT_SEL1	0x403000C4	FULL	Port selection 1

16.14 PRT 13

Register Name	Address	Permission	Description
HSIOM_PRT13_PORT_SEL0	0x403000D0	FULL	Port selection 0
HSIOM_PRT13_PORT_SEL1	0x403000D4	FULL	Port selection 1

16.15 PRT 14

Register Name	Address	Permission	Description
HSIOM_PRT14_PORT_SEL0	0x403000E0	FULL	Port selection 0
HSIOM_PRT14_PORT_SEL1	0x403000E4	FULL	Port selection 1

16.16 PRT 15

Register Name	Address	Permission	Description
HSIOM_PRT15_PORT_SEL0	0x403000F0	FULL	Port selection 0

16.17 PRT 16

Register Name	Address	Permission	Description
HSIOM_PRT16_PORT_SEL0	0x40300100	FULL	Port selection 0
HSIOM_PRT16_PORT_SEL1	0x40300104	FULL	Port selection 1

16.18 PRT 17

Register Name	Address	Permission	Description
HSIOM_PRT17_PORT_SEL0	0x40300110	FULL	Port selection 0
HSIOM_PRT17_PORT_SEL1	0x40300114	FULL	Port selection 1

16.19 PRT 18

Register Name	Address	Permission	Description
HSIOM_PRT18_PORT_SEL0	0x40300120	FULL	Port selection 0
HSIOM_PRT18_PORT_SEL1	0x40300124	FULL	Port selection 1

16.20 PRT 19

Register Name	Address	Permission	Description
HSIOM_PRT19_PORT_SEL0	0x40300130	FULL	Port selection 0

Register Name	Address	Permission	Description
HSIOM_PRT19_PORT_SEL1	0x40300134	FULL	Port selection 1 Note:IO5_SEL IO6_SEL IO7_SEL are not available for this register

16.21 PRT 20

Register Name	Address	Permission	Description
HSIOM_PRT20_PORT_SEL0	0x40300140	FULL	Port selection 0
HSIOM_PRT20_PORT_SEL1	0x40300144	FULL	Port selection 1

16.22 PRT 21

Register Name	Address	Permission	Description
HSIOM_PRT21_PORT_SEL0	0x40300150	FULL	Port selection 0
HSIOM_PRT21_PORT_SEL1	0x40300154	FULL	Port selection 1

16.23 PRT 22

Register Name	Address	Permission	Description
HSIOM_PRT22_PORT_SEL0	0x40300160	FULL	Port selection 0
HSIOM_PRT22_PORT_SEL1	0x40300164	FULL	Port selection 1

16.24 PRT 23

Register Name	Address	Permission	Description
HSIOM_PRT23_PORT_SEL0	0x40300170	FULL	Port selection 0
HSIOM_PRT23_PORT_SEL1	0x40300174	FULL	Port selection 1

16.25 PRT 24

Register Name	Address	Permission	Description
HSIOM_PRT24_PORT_SEL0	0x40300180	FULL	Port selection 0
HSIOM_PRT24_PORT_SEL1	0x40300184	FULL	Port selection 1 Note:IO5_SEL IO6_SEL IO7_SEL are not available for this register

16.26 PRT 25

Register Name	Address	Permission	Description
HSIOM_PRT25_PORT_SEL0	0x40300190	FULL	Port selection 0
HSIOM_PRT25_PORT_SEL1	0x40300194	FULL	Port selection 1

16.27 PRT 26

Register Name	Address	Permission	Description
HSIOM_PRT26_PORT_SEL0	0x403001A0	FULL	Port selection 0
HSIOM_PRT26_PORT_SEL1	0x403001A4	FULL	Port selection 1

16.28 PRT 27

Register Name	Address	Permission	Description
HSIOM_PRT27_PORT_SEL0	0x403001B0	FULL	Port selection 0
HSIOM_PRT27_PORT_SEL1	0x403001B4	FULL	Port selection 1

16.29 PRT 28

Register Name	Address	Permission	Description
HSIOM_PRT28_PORT_SEL0	0x403001C0	FULL	Port selection 0
HSIOM_PRT28_PORT_SEL1	0x403001C4	FULL	Port selection 1

16.30 PRT 29

Register Name	Address	Permission	Description
HSIOM_PRT29_PORT_SEL0	0x403001D0	FULL	Port selection 0
HSIOM_PRT29_PORT_SEL1	0x403001D4	FULL	Port selection 1

16.31 PRT 30

Register Name	Address	Permission	Description
HSIOM_PRT30_PORT_SEL0	0x403001E0	FULL	Port selection 0

16.32 PRT 31

Register Name	Address	Permission	Description
HSIOM_PRT31_PORT_SEL0	0x403001F0	FULL	Port selection 0 Note: IO3_SEL is not available for this register

16.33 PRT 32

Register Name	Address	Permission	Description
HSIOM_PRT32_PORT_SEL0	0x40300200	FULL	Port selection 0
HSIOM_PRT32_PORT_SEL1	0x40300204	FULL	Port selection 1

16.34 Register Details

16.34.1 HSIOM_AMUX_SPLIT_CTL

Description: AMUX splitter cell control

Address: 0x40302000

Offset: 0x2000

Retention: Retained

IsDeepSleep: No

Comment: This register controls the breaking of AMUX buses A and B into multiple segments. It allows for grounding, disconnecting and feeding through. Feeding through is be done straight (from Left segment AMUXBUSA/AMUXBUSB to Right segment AMUXBUSA/AMUXBUSB).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	SWITCH_BB_S0 [6:6]	SWITCH_BB_SR [5:5]	SWITCH_BB_SL [4:4]	None [3:3]	SWITCH_AA_S0 [2:2]	SWITCH_AA_SR [1:1]	SWITCH_AA_SL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SWITCH_AA_SL	RW	RW	0	T-switch control for Left AMUXBUSA switch: '0': switch open. '1': switch closed.
1	SWITCH_AA_SR	RW	RW	0	T-switch control for Right AMUXBUSA switch: '0': switch open. '1': switch closed.
2	SWITCH_AA_S0	RW	RW	0	T-switch control for AMUXBUSA vssa/ground switch: '0': switch open. '1': switch closed.
4	SWITCH_BB_SL	RW	RW	0	T-switch control for Left AMUXBUSB switch.
5	SWITCH_BB_SR	RW	RW	0	T-switch control for Right AMUXBUSB switch.
6	SWITCH_BB_S0	RW	RW	0	T-switch control for AMUXBUSB vssa/ground switch.

16.34.2 HSIOM_MONITOR_CTL_0

Description: Power/Ground Monitor cell control 0
Address: 0x40302200
Offset: 0x2200
Retention: Retained
IsDeepSleep: No
Comment: This register controls the connectivity of PWR/GND monitor cells to either AMUX bus A or B respectively.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MONITOR_EN [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MONITOR_EN [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	MONITOR_EN [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	MONITOR_EN [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	MONITOR_EN	RW	RW	0	control for switch, which connects the power/ground supply to AMUXBUS_A/B respectively when switch is closed: '0': switch open. '1': switch closed.

16.34.3 HSIOM_ALT_JTAG_EN

Description: Alternate JTAG IF selection register
Address: 0x40302240
Offset: 0x2240
Retention: Retained
IsDeepSleep: No
Comment: This register provides the alternate JTAG interface selection
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLE	RW	RW	0	Provides the selection for alternate JTAG IF connectivity. 0: Primary JTAG interface is selected 1: Secondary (alternate) JTAG interface is selected. This connectivity works ONLY in ACTIVE mode.

16.34.4 PRT

16.34.4.1 HSIOM_PRT_PORT_SEL0

Description: Port selection 0

Address: 0x40300000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: The High Speed IO Mux (HSIOM) selects the hardware peripheral connection to an IO pin. The default setting of 'GPIO' leaves the pin under CPU control through firmware. Pin specific connections for the 'DS_x' and 'ACT_x' settings are listed in the pinout section of the device datasheet.

Note: when initializing IO's that are connected to a live bus (such as I2C), make sure the peripheral and HSIOM is properly configured (HSIOM_PRT_SELx) before turning the IO on (GPIO_PRT_CFG.DRIVE_MODEx) to avoid producing glitches on the bus.

Note: peripherals other than GPIO & UDB/DSI directly control both the output and output-enable of the output buffer (peripherals can drive strong 0 or strong 1 in any mode except OFF='0').

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			IO0_SEL [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			IO1_SEL [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			IO2_SEL [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			IO3_SEL [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	IO0_SEL	RW	RW	0	Selects connection for IO pin 0 route.
	GPIO			0	GPIO controls 'out'
	GPIO_DSI			1	GPIO controls 'out', DSI controls 'output enable'
	DSI_DSI			2	DSI controls 'out' and 'output enable'
	DSI_GPIO			3	DSI controls 'out', GPIO controls 'output enable'
	AMUXA			4	Analog mux bus A
	AMUXB			5	Analog mux bus B
	AMUXA_DSI			6	Analog mux bus A, DSI control
	AMUXB_DSI			7	Analog mux bus B, DSI control
	ACT_0			8	Active functionality 0
	ACT_1			9	Active functionality 1
	ACT_2			10	Active functionality 2
	ACT_3			11	Active functionality 3
	DS_0			12	DeepSleep functionality 0
	DS_1			13	DeepSleep functionality 1
	DS_2			14	DeepSleep functionality 2
	DS_3			15	DeepSleep functionality 3
	ACT_4			16	Active functionality 4
	ACT_5			17	Active functionality 5
	ACT_6			18	Active functionality 6
	ACT_7			19	Active functionality 7

Bits	Name	SW	HW	Default or Enum	Description
	ACT_8			20	Active functionality 8
	ACT_9			21	Active functionality 9
	ACT_10			22	Active functionality 10
	ACT_11			23	Active functionality 11
	ACT_12			24	Active functionality 12
	ACT_13			25	Active functionality 13
	ACT_14			26	Active functionality 14
	ACT_15			27	Active functionality 15
	DS_4			28	DeepSleep functionality 4
	DS_5			29	DeepSleep functionality 5
	DS_6			30	DeepSleep functionality 6
	DS_7			31	DeepSleep functionality 7
8:12	IO1_SEL	RW	RW	0	Selects connection for IO pin 1 route.
16:20	IO2_SEL	RW	RW	0	Selects connection for IO pin 2 route.
24:28	IO3_SEL	RW	RW	0	Selects connection for IO pin 3 route.

16.34.4.2 HSIOM_PRT_PORT_SEL1

Description: Port selection 1
Address: 0x40300004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: See PORT_SEL0 for details
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			IO4_SEL [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			IO5_SEL [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			IO6_SEL [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			IO7_SEL [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	IO4_SEL	RW	RW	0	Selects connection for IO pin 4 route. See PORT_SEL0 for connection details.
8:12	IO5_SEL	RW	RW	0	Selects connection for IO pin 5 route.
16:20	IO6_SEL	RW	RW	0	Selects connection for IO pin 6 route.
24:28	IO7_SEL	RW	RW	0	Selects connection for IO pin 7 route.

17 I2S

17.1 I2S 0

Description I2S registers
Base Address 0x40800000
Size 0x1000
Slave Num MMIO8 - 0

Register Name	Address	Permission	Description
I2S0_CTL	0x40800000	FULL	Control
I2S0_CLOCK_CTL	0x40800010	FULL	Clock control
I2S0_CLOCK_STAT	0x40800014	FULL	Clock Status
I2S0_CMD	0x40800020	FULL	Command
I2S0_TR_CTL	0x40800040	FULL	Trigger control
I2S0_TX_CTL	0x40800080	FULL	Transmitter control
I2S0_TX_WATCHDOG	0x40800084	FULL	Transmitter watchdog
I2S0_RX_CTL	0x408000A0	FULL	Receiver control
I2S0_RX_WATCHDOG	0x408000A4	FULL	Receiver watchdog
I2S0_TX_FIFO_CTL	0x40800200	FULL	TX FIFO control
I2S0_TX_FIFO_STATUS	0x40800204	FULL	TX FIFO status
I2S0_TX_FIFO_WR	0x40800208	FULL	TX FIFO write
I2S0_RX_FIFO_CTL	0x40800300	FULL	RX FIFO control
I2S0_RX_FIFO_STATUS	0x40800304	FULL	RX FIFO status
I2S0_RX_FIFO_RD	0x40800308	FULL	RX FIFO read
I2S0_RX_FIFO_RD_SILENT	0x4080030C	FULL	RX FIFO silent read
I2S0_INTR	0x40800F00	FULL	Interrupt register
I2S0_INTR_SET	0x40800F04	FULL	Interrupt set register
I2S0_INTR_MASK	0x40800F08	FULL	Interrupt mask register
I2S0_INTR_MASKED	0x40800F0C	FULL	Interrupt masked register

17.2 I2S 1

Description I2S registers
Base Address 0x40801000
Size 0x1000
Slave Num MMIO8 - 1

Register Name	Address	Permission	Description
I2S1_CTL	0x40801000	FULL	Control
I2S1_CLOCK_CTL	0x40801010	FULL	Clock control
I2S1_CLOCK_STAT	0x40801014	FULL	Clock Status
I2S1_CMD	0x40801020	FULL	Command
I2S1_TR_CTL	0x40801040	FULL	Trigger control
I2S1_TX_CTL	0x40801080	FULL	Transmitter control
I2S1_TX_WATCHDOG	0x40801084	FULL	Transmitter watchdog
I2S1_RX_CTL	0x408010A0	FULL	Receiver control
I2S1_RX_WATCHDOG	0x408010A4	FULL	Receiver watchdog
I2S1_TX_FIFO_CTL	0x40801200	FULL	TX FIFO control
I2S1_TX_FIFO_STATUS	0x40801204	FULL	TX FIFO status
I2S1_TX_FIFO_WR	0x40801208	FULL	TX FIFO write
I2S1_RX_FIFO_CTL	0x40801300	FULL	RX FIFO control
I2S1_RX_FIFO_STATUS	0x40801304	FULL	RX FIFO status
I2S1_RX_FIFO_RD	0x40801308	FULL	RX FIFO read
I2S1_RX_FIFO_RD_SILENT	0x4080130C	FULL	RX FIFO silent read
I2S1_INTR	0x40801F00	FULL	Interrupt register
I2S1_INTR_SET	0x40801F04	FULL	Interrupt set register
I2S1_INTR_MASK	0x40801F08	FULL	Interrupt mask register
I2S1_INTR_MASKED	0x40801F0C	FULL	Interrupt masked register

17.3 I2S 2

Description I2S registers
Base Address 0x40802000

Size 0x1000
Slave Num MMIO8 - 2

Register Name	Address	Permission	Description
I2S2_CTL	0x40802000	FULL	Control
I2S2_CLOCK_CTL	0x40802010	FULL	Clock control
I2S2_CLOCK_STAT	0x40802014	FULL	Clock Status
I2S2_CMD	0x40802020	FULL	Command
I2S2_TR_CTL	0x40802040	FULL	Trigger control
I2S2_TX_CTL	0x40802080	FULL	Transmitter control
I2S2_TX_WATCHDOG	0x40802084	FULL	Transmitter watchdog
I2S2_RX_CTL	0x408020A0	FULL	Receiver control
I2S2_RX_WATCHDOG	0x408020A4	FULL	Receiver watchdog
I2S2_TX_FIFO_CTL	0x40802200	FULL	TX FIFO control
I2S2_TX_FIFO_STATUS	0x40802204	FULL	TX FIFO status
I2S2_TX_FIFO_WR	0x40802208	FULL	TX FIFO write
I2S2_RX_FIFO_CTL	0x40802300	FULL	RX FIFO control
I2S2_RX_FIFO_STATUS	0x40802304	FULL	RX FIFO status
I2S2_RX_FIFO_RD	0x40802308	FULL	RX FIFO read
I2S2_RX_FIFO_RD_SILENT	0x4080230C	FULL	RX FIFO silent read
I2S2_INTR	0x40802F00	FULL	Interrupt register
I2S2_INTR_SET	0x40802F04	FULL	Interrupt set register
I2S2_INTR_MASK	0x40802F08	FULL	Interrupt mask register
I2S2_INTR_MASKED	0x40802F0C	FULL	Interrupt masked register

17.4 Register Details

17.4.1 I2S_CTL

Description: Control
Address: 0x40800000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control I2S block.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	RX_ENABLED [31:31]	TX_ENABLED [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	TX_ENABLED	RW	RW	0	Enables the I2S TX component: '0': Disabled. '1': Enabled.
31	RX_ENABLED	RW	RW	0	Enables the I2S RX component: '0': Disabled. '1': Enabled.

17.4.2 I2S_CLOCK_CTL

Description: Clock control
Address: 0x40800010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: This register can configure frequencies for I2S block and master clock. This register should NOT be changed during communication.
Default: 0x3000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CLOCK_DIV [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		MCLK_DIV [13:12]		None [11:9]			CLOCK_SEL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							MCLK_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	CLOCK_DIV	RW	RW	0	Frequency divisor for generating I2S clock frequency. The selected clock with CLOCK_SEL is divided by this. '0': Bypass '1': 2 x '2': 3 x '3': 4 x ... '62': 63 x '63': 64 x
8	CLOCK_SEL	RW	RW	0	Selects clock to be used by I2S: '0': Internal clock ('clk_audio_i2s') '1': External clock ('clk_i2s_if')
12:13	MCLK_DIV	RW	RW	3	Selects clock divider for MCLK_OUT. CTL.TX_ENABLED=1 or CTL.RX_ENABLED=1 and and CLOCK_CTL.CLOCK_SEL=0 to enable the clock.
	DIV1			0	Divide clk_audio_i2s by 1 (Bypass)
	DIV2			1	Divide clk_audio_i2s by 2
	DIV4			2	Divide clk_audio_i2s by 4
	DIV8			3	Divide clk-audio_i2s by 8
16	MCLK_EN	RW	RW	0	Enable MCLK - enables MCLK divider operation Upon assertion allows MCLK Divider to begin operation. Upon de-assertion, i.e. 1-0 transition, allows MCLK divider to reach the all 0s state (reset state) then freezes the divider. This permits a controlled power-on/power-off sequence that may be used prior to going to DeepSleep/IP Disable and avoids glitching the MCLK.

17.4.3 I2S_CLOCK_STAT

Description: Clock Status
Address: 0x40800014
Offset: 0x14
Retention: Not Retained
IsDeepSleep: No
Comment: This register indicates the status of the MCLK Divider and is used to allow a controlled shutdown of the clock.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							MCLK_DIV_OFF [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MCLK_DIV_OFF	R	R	0	MCLK Divider OFF 0: Indicates MCLK Divider not a reset state 1: Indicates MCLK Divider at reset state. This is ONLY set when IP is enabled (CTL.RX_ENABLED=1 or CTL.TX_ENABLED=1), CLOCK_CTL.MCLK_EN=0, and MCLK_DIV reaches it's reset state. The intent is that this bit indicates successful shutdown of the MCLK_DIVIDER after CLOCK_CTL.MCLK_EN transitions from 1 to 0.

17.4.4 I2S_CMD

Description: Command
Address: 0x40800020
Offset: 0x20
Retention: Not Retained
IsDeepSleep: No
Comment: This register can control I2S functions.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							TX_START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							TX_PAUSE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							RX_START [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_START	RW	RW	0	Transmitter enable: '0': Disabled. '1': Enabled.
8	TX_PAUSE	RW	RW	0	Pause enable: '0': Disabled (TX FIFO data is sent over I2S). '1': Enabled ('0' data is sent over I2S, instead of TX FIFO data).
16	RX_START	RW	RW	0	Receiver enable: '0': Disabled. '1': Enabled.

17.4.5 I2S_TR_CTL

Description: Trigger control
Address: 0x40800040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: This register can enable DMA for I2S. This register should NOT be changed during communication.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							TX_REQ_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							RX_REQ_EN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_REQ_EN	RW	RW	0	Trigger output ('tr_i2s_tx_req') enable for requests of DMA transfer in transmission '0': Disabled. '1': Enabled.
16	RX_REQ_EN	RW	RW	0	Trigger output ('tr_i2s_rx_req') enable for requests of DMA transfer in reception '0': Disabled. '1': Enabled.

17.4.6 I2S_TX_CTL

Description: Transmitter control
Address: 0x40800080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment: This register can configure transmitter for I2S functions. This register should NOT be changed during communication.
Default: 0x440510

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MS [7:7]	CH_NR [6:4]			B_CLOCK_INV [3:3]	None [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		WD_EN [13:13]	OVHDATA [12:12]	None [11:11]	WS_PULSE [10:10]	I2S_MODE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	WORD_LEN [22:20]			None [19:19]	CH_LEN [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						SCKI_POL [25:25]	SCKO_POL [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3	B_CLOCK_INV	RW	RW	0	Serial data transmission is advanced by 0.5 SCK cycles. This bit is valid only in TX slave mode. When set to '1', the serial data will be transmitted 0.5 SCK cycles earlier than when set to '0'. 1) TX_CTL.SCKI_POL=0 and TX_CTL.B_CLOCK_INV=0: Serial data will be transmitted off the SCK falling edge 2) TX_CTL.SCKI_POL=0 and TX_CTL.B_CLOCK_INV=1: Serial data will be transmitted off the SCK rising edge that is 0.5 SCK cycles before the SCK falling edge in 1) 3) TX_CTL.SCKI_POL=1 and TX_CTL.B_CLOCK_INV=0: Serial data will be transmitted off the SCK rising edge 4) TX_CTL.SCKI_POL=1 and TX_CTL.B_CLOCK_INV=1: Serial data will be transmitted off the SCK falling edge that is 0.5 SCK cycles before the SCK rising edge in 3) (Note that this is only the appearance w.r.t. SCK edge, the actual timing is generated by an internal clock that runs 8x the SCK frequency). The word sync (TX_WS) signal is not affected by this bit setting. Note: When Master mode, must be '0'. (Note: This bit is connected to AR38U12.TX_CFG.TX_BCLKINV)
	FALLING_EDGE_TX			0	SDO transmitted at SCK falling edge when TX_CTL.SCKI_POL=0
	RISING_EDGE_TX			1	SDO transmitted at SCK rising edge when TX_CTL.SCKI_POL=0

Bits	Name	SW	HW	Default or Enum	Description
4:6	CH_NR	RW	RW	1	Specifies number of channels per frame: Note: only '2channels' is supported during Left Justified or I2S mode. Hence software must set '1' to this field in the modes. (Note: These bits are connected to AR38U12.TX_CFG.TX_CHSET)
	CH_NUM1			0	1 channel
	CH_NUM2			1	2 channels
	CH_NUM3			2	3 channels
	CH_NUM4			3	4 channels
	CH_NUM5			4	5 channels
	CH_NUM6			5	6 channels
	CH_NUM7			6	7 channels
	CH_NUM8			7	8 channels
7	MS	RW	RW	0	Set interface in master or slave mode: (Note: This bit is connected to AR38U12.TX_CFG.TX_MS)
	SLAVE			0	Slave
	MASTER			1	Master
8:9	I2S_MODE	RW	RW	1	Select I2S, left-justified or TDM: (Note: These bits are connected to AR38U12.TX_CFG.TX_I2S_MODE)
	LEFT_JUSTIFIED			0	Left Justified
	I2S			1	I2S mode
	TDM_A			2	TDM mode A, the 1st Channel align to WSO Rising Edge
	TDM_B			3	TDM mode B, the 1st Channel align to WSO Rising edge with 1 SCK Delay
10	WS_PULSE	RW	RW	1	Set WS pulse width in TDM mode: (Note: This bit is connected to AR38U12.TX_CFG.TX_WS_PULSE) Note: When not TDM mode, must be '1'.
	SCK_PERIOD			0	Pulse width is 1 SCK period
	CH_LENGTH			1	Pulse width is 1 channel length
12	OVHDATA	RW	RW	0	Set overhead value: '0': Set to '0' '1': Set to '1' (Note: This bit is connected to AR38U12.TX_CFG.TX_OVHDATA)
13	WD_EN	RW	RW	0	Set watchdog for 'tx_ws_in': '0': Disabled. '1': Enabled.
16:18	CH_LEN	RW	RW	4	Channel length in number of bits: Note: - When this field is configured to '6' or '7', the length is set to 32-bit (same as '5'). - When TDM mode, must be 32-bit length to this field. (Note: These bits are connected to AR38U12.TX_CFG.TX_CHLEN)
	BIT_LEN8			0	8-bit
	BIT_LEN16			1	16-bit
	BIT_LEN18			2	18-bit
	BIT_LEN20			3	20-bit

Bits	Name	SW	HW	Default or Enum	Description
	BIT_LEN24			4	24-bit
	BIT_LEN32			5	32-bit
20:22	WORD_LEN	RW	RW	4	Word length in number of bits: Note: - When this field is configured to '6' or '7', the length is set to 32-bit (same as '5'). - Don't configure this field as beyond Channel length. (Note: These bits are connected to AR38U12.TX_CFG.TX_IWL)
	BIT_LEN8			0	8-bit
	BIT_LEN16			1	16-bit
	BIT_LEN18			2	18-bit
	BIT_LEN20			3	20-bit
	BIT_LEN24			4	24-bit
	BIT_LEN32			5	32-bit
24	SCKO_POL	RW	RW	0	TX master bit clock polarity. When this bit is 1, the outgoing tx_sck signal is inverted after it has been transmitted from the I2S transceiver core. This bit does not affect the internal serial data transmission timing. The word sync (TX_WS) signal is not affected by this bit setting. '0': When transmitter is in master mode, serial data is transmitted from the falling bit clock edge '1': When transmitter is in master mode, serial data is transmitted from the rising bit clock edge
25	SCKI_POL	RW	RW	0	TX slave bit clock polarity. When this bit is 1, the incoming tx_sck signal is inverted before it is received by the I2S transceiver core. This bit does not affect the internal serial data transmission timing. The word sync (TX_WS) signal is not affected by this bit setting. See TX_CTL.B_CLOCK_INV for more details.

17.4.7 I2S_TX_WATCHDOG

Description: Transmitter watchdog
Address: 0x40800084
Offset: 0x84
Retention: Retained
IsDeepSleep: No
Comment: This register can configure counter value for the Tx watchdog. This register should NOT be changed during the operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WD_COUNTER [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	WD_COUNTER [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	WD_COUNTER [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	WD_COUNTER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	WD_COUNTER	RW	RW	0	Start value of the TX watchdog. With the reset value of 0x0000:0000 the counter is disabled. This is clocked by the AHB-Lite system clock 'clk_sys'.

17.4.8 I2S_RX_CTL

Description: Receiver control
Address: 0x408000A0
Offset: 0xA0
Retention: Retained
IsDeepSleep: No
Comment: This register should NOT be changed during communication.
Default: 0x440510

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MS [7:7]	CH_NR [6:4]			B_CLOCK_INV [3:3]	None [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		WD_EN [13:13]	None [12:11]		WS_PULSE [10:10]	I2S_MODE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	BIT_EXTENSION [23:23]	WORD_LEN [22:20]			None [19:19]	CH_LEN [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						SCKI_POL [25:25]	SCKO_POL [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
3	B_CLOCK_INV	RW	RW	0	Serial data capture is delayed by 0.5 SCK cycles. This bit is valid only in RX master mode. When set to '1', the serial data will be captured 0.5 SCK cycles later than when set to '0'. 1) RX_CTL.SCKO_POL=0 and RX_CTL.B_CLOCK_INV=0: Serial data will be captured by the SCK rising edge 2) RX_CTL.SCKO_POL=0 and RX_CTL.B_CLOCK_INV=1: Serial data will be captured by the SCK falling edge that is 0.5 SCK cycles after the SCK rising edge in 1) 3) RX_CTL.SCKO_POL=1 and RX_CTL.B_CLOCK_INV=0: Serial data will be captured by the SCK falling edge 4) RX_CTL.SCKO_POL=1 and RX_CTL.B_CLOCK_INV=1: Serial data will be captured by the SCK rising edge that is 0.5 SCK cycles after the SCK falling edge in 3) (Note that this is only the appearance w.r.t. SCK edge, the actual capture timing is derived from an internal clock that runs 8x the SCK frequency). The word sync (RX_WS) signal is not affected by this bit setting. Note: When Slave mode, must be '0'. (Note: This bit is connected to AR38U12.TX_CFG.RX_BCLKINV)
	RISING_EDGE_RX			0	SDI received at SCK rising edge when RX_CTL.SCKO_POL=0
	FALLING_EDGE_RX			1	SDI received at SCK falling edge when RX_CTL.SCKO_POL=0

Bits	Name	SW	HW	Default or Enum	Description
4:6	CH_NR	RW	RW	1	Specifies number of channels per frame: Note: only '2channels' is supported during Left Justified or I2S mode. Hence software must set '1' to this field in the modes. (Note: These bits are connected to AR38U12.RX_CFG.RX_CHSET)
	CH_NUM1			0	1 channel
	CH_NUM2			1	2 channels
	CH_NUM3			2	3 channels
	CH_NUM4			3	4 channels
	CH_NUM5			4	5 channels
	CH_NUM6			5	6 channels
	CH_NUM7			6	7 channels
	CH_NUM8			7	8 channels
7	MS	RW	RW	0	Set interface in master or slave mode: (Note: This bit is connected to AR38U12.TX_CFG.RX_MS)
	SLAVE			0	Slave
	MASTER			1	Master
8:9	I2S_MODE	RW	RW	1	Select I2S, left-justified or TDM: (Note: These bits are connected to AR38U12.RX_CFG.RX_I2S_MODE)
	LEFT_JUSTIFIED			0	Left Justified
	I2S			1	I2S mode
	TDM_A			2	TDM mode A, the 1st Channel align to WSO Rising Edge
	TDM_B			3	TDM mode B, the 1st Channel align to WSO Rising edge with 1 SCK Delay
10	WS_PULSE	RW	RW	1	Set WS pulse width in TDM mode: (Note: This bit is connected to AR38U12.RX_CFG.RX_WS_PULSE) Note: When not TDM mode, must be '1'.
	SCK_PERIOD			0	Pulse width is 1 SCK period
	CH_LENGTH			1	Pulse width is 1 channel length
13	WD_EN	RW	RW	0	Set watchdog for 'rx_ws_in' '0': Disabled. '1': Enabled.
16:18	CH_LEN	RW	RW	4	Channel length in number of bits: Note: - When this field is configured to '6' or '7', the length is set to 32-bit (same as '5'). - When TDM mode, must be 32-bit length to this field. (Note: These bits are connected to AR38U12.RX_CFG.RX_CHLEN)
	BIT_LEN8			0	8-bit
	BIT_LEN16			1	16-bit
	BIT_LEN18			2	18-bit
	BIT_LEN20			3	20-bit
	BIT_LEN24			4	24-bit
	BIT_LEN32			5	32-bit

Bits	Name	SW	HW	Default or Enum	Description
20:22	WORD_LEN	RW	RW	4	Word length in number of bits: Note: - When this field is configured to '6' or '7', the length is set to 32-bit (same as '5'). - Don't configure this field as beyond Channel length. (Note: These bits are connected to AR38U12.RX_CFG.RX_IWL)
	BIT_LEN8			0	8-bit
	BIT_LEN16			1	16-bit
	BIT_LEN18			2	18-bit
	BIT_LEN20			3	20-bit
	BIT_LEN24			4	24-bit
	BIT_LEN32			5	32-bit
23	BIT_EXTENSION	RW	RW	0	When reception word length is shorter than the word length of RX_FIFO_RD, extension mode of upper bit should be set. '0': Extended by '0' '1': Extended by sign bit (if MSB word is '1', then it is extended by '1', if MSB is '0' then it is extended by '0')
24	SCKO_POL	RW	RW	0	RX master bit clock polarity. When this bit is 1, the outgoing rx_sck signal is inverted after it has been transmitted from the I2S receiver core. This bit does not affect the internal serial data capture timing. The word sync (RX_WS) signal is not affected by this bit setting. See RX_CTL.B_CLOCK_INV for more details.
25	SCKI_POL	RW	RW	0	RX slave bit clock polarity. When this bit is 1, the incoming rx_sck signal is inverted before it is received by the I2S receiver core. This bit does not affect the internal serial data capture timing. The word sync (RX_WS) signal is not affected by this bit setting. '0': When receiver is in slave mode, serial data is sampled on the rising bit clock edge '1': When receiver is in slave mode, serial data is sampled on the falling bit clock edge

17.4.9 I2S_RX_WATCHDOG

Description: Receiver watchdog
Address: 0x408000A4
Offset: 0xA4
Retention: Retained
IsDeepSleep: No
Comment: This register should NOT be changed during the operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WD_COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	WD_COUNTER [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WD_COUNTER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WD_COUNTER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	WD_COUNTER	RW	RW	0	Start value of the RX watchdog. With the reset value of 0x0000:0000 the counter is disabled. This is clocked by the AHB-Lite system clock 'clk_sys'.

17.4.10 I2S_TX_FIFO_CTL

Description: TX FIFO control
Address: 0x40800200
Offset: 0x200
Retention: Not Retained
IsDeepSleep: No
Comment: This register can configure FIFO for I2S .
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGGER_LEVEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FREEZE [17:17]	CLEAR [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGGER_LEVEL	RW	RW	0	Trigger level. When the TX FIFO has less entries than the number of this field, a transmitter trigger event is generated.
16	CLEAR	RW	RW	0	When '1', the TX FIFO and TX_BUF are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period.
17	FREEZE	RW	RW	0	When '1', hardware reads from the TX FIFO do not remove FIFO entries. Freeze will not advance the TX FIFO read pointer. This field is used only for debugging purposes.

17.4.11 I2S_TX_FIFO_STATUS

Description: TX FIFO status
Address: 0x40800204
Offset: 0x204
Retention: Not Retained
IsDeepSleep: No
Comment: This register displays the statuses of FIFO for I2S.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	USED [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							USED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RD_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WR_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	USED	R	R	0	Number of entries in the TX FIFO. The field value is in the range [0, 256].
16:23	RD_PTR	R	R	0	TX FIFO read pointer: FIFO location from which a data frame is read by the hardware. This field is used only for debugging purposes.
24:31	WR_PTR	R	R	0	TX FIFO write pointer: FIFO location at which a new data frame is written by the host. This field is used only for debugging purposes.

17.4.12 I2S_TX_FIFO_WR

Description: TX FIFO write
Address: 0x40800208
Offset: 0x208
Retention: Not Retained
IsDeepSleep: No
Comment: This register stores transmission data for I2S transfer.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	W	W	0	Data written into the TX FIFO. Behavior is similar to that of a PUSH operation. Note: Don't access to this register while TX_FIFO_CTL.CLEAR is '1'.

17.4.13 I2S_RX_FIFO_CTL

Description: RX FIFO control
Address: 0x40800300
Offset: 0x300
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGGER_LEVEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FREEZE [17:17]	CLEAR [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGGER_LEVEL	RW	RW	0	Trigger level. When the RX FIFO has more entries than the number of this field, a receiver trigger event is generated. Note: software can configure up to 253 in I2S mode or Left Justified (RX_CTL.I2S_MODE = '0' or '1'). In TDM mode (RX_CTL.I2S_MODE = '2' or '3'), it can configure up to [256 - (RX_CTL.CH_NR+2)].
16	CLEAR	RW	RW	0	When '1', the RX FIFO and RX_BUF are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period.
17	FREEZE	RW	RW	0	When '1', hardware writes to the RX FIFO have no effect. Freeze will not advance the RX FIFO write pointer. This field is used only for debugging purpose.

17.4.14 I2S_RX_FIFO_STATUS

Description: RX FIFO status
Address: 0x40800304
Offset: 0x304
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	USED [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							USED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RD_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WR_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	USED	R	R	0	Number of entries in the RX FIFO. The field value is in the range [0, 256].
16:23	RD_PTR	R	R	0	RX FIFO read pointer: FIFO location from which a data frame is read by the host. This field is used only for debugging purposes.
24:31	WR_PTR	R	R	0	RX FIFO write pointer: FIFO location at which a new data frame is written by the hardware. This field is used only for debugging purposes.

17.4.15 I2S_RX_FIFO_RD

Description: RX FIFO read
Address: 0x40800308
Offset: 0x308
Retention: Not Retained
IsDeepSleep: No
Comment: When the IP is disabled (CTRL.RX_ENABLED is '0'), a read from this register returns 0xffff.ffff.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	0	Data read from the RX FIFO. Reading a data frame will remove the data frame from the RX FIFO; i.e. behavior is similar to that of a POP operation. Notes: - Don't access to this register while RX_FIFO_CTL.CLEAR is '1'. - Two stored data may be not valid after CMD.RX_START is set '1'. Therefore we recommend software discard those data.

17.4.16 I2S_RX_FIFO_RD_SILENT

Description: RX FIFO silent read
Address: 0x4080030C
Offset: 0x30C
Retention: Not Retained
IsDeepSleep: No
Comment: This register stores received data for I2S transfer. When the IP is disabled (CTRL.RX_ENABLED is '0'), a read from this register returns 0xffff:ffff.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	0	Data read from the RX FIFO. Reading a data frame will NOT remove the data frame from the RX FIFO; i.e. behavior is similar to that of a PEEK operation. This field is used only for debugging purposes. Notes: - Don't access to this register while RX_FIFO_CTL.CLEAR is '1'. - Two stored data may be not valid after CMD.RX_START is set '1'. Therefore we recommend software discard those data.

17.4.17 I2S_INTR

Description: Interrupt register
Address: 0x40800F00
Offset: 0xF00
Retention: Not Retained
IsDeepSleep: No
Comment: This register displays the interrupt status.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	TX_UNDERFLOW [6:6]	TX_OVERFLOW [5:5]	TX_EMPTY [4:4]	None [3:2]		TX_NOT_FULL [1:1]	TX_TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							TX_WD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	RX_UNDERFLOW [22:22]	RX_OVERFLOW [21:21]	None [20:20]	RX_FULL [19:19]	RX_NOT_EMPTY [18:18]	None [17:17]	RX_TRIGGER [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							RX_WD [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_TRIGGER	RW1C	RW1C	0	Less entries in the TX FIFO than the value specified by TRIGGER_LEVEL in TX_FIFO_CTRL.
1	TX_NOT_FULL	RW1C	RW1C	0	TX FIFO is not full.
4	TX_EMPTY	RW1C	RW1C	0	TX FIFO is empty; i.e. it has 0 entries.
5	TX_OVERFLOW	RW1C	RW1C	0	Attempt to write to a full TX FIFO.
6	TX_UNDERFLOW	RW1C	RW1C	0	Attempt to read from an empty TX FIFO. This happens when the IP is ready to transfer data and TX_EMPTY is '1'.
8	TX_WD	RW1C	RW1C	0	Triggers (sets to '1') when the Tx watchdog event occurs.
16	RX_TRIGGER	RW1C	RW1C	0	More entries in the RX FIFO than the value specified by TRIGGER_LEVEL in RX_FIFO_CTRL.
18	RX_NOT_EMPTY	RW1C	RW1C	0	RX FIFO is not empty.
19	RX_FULL	RW1C	RW1C	0	RX FIFO is full.
21	RX_OVERFLOW	RW1C	RW1C	0	Attempt to write to a full RX FIFO.
22	RX_UNDERFLOW	RW1C	RW1C	0	Attempt to read from an empty RX FIFO.
24	RX_WD	RW1C	RW1C	0	Triggers (sets to '1') when the Rx watchdog event occurs.

17.4.18 I2S_INTR_SET

Description: Interrupt set register
Address: 0x40800F04
Offset: 0xF04
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	TX_UNDERFLOW [6:6]	TX_OVERFLOW [5:5]	TX_EMPTY [4:4]	None [3:2]		TX_NOT_FULL [1:1]	TX_TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							TX_WD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	RX_UNDERFLOW [22:22]	RX_OVERFLOW [21:21]	None [20:20]	RX_FULL [19:19]	RX_NOT_EMPTY [18:18]	None [17:17]	RX_TRIGGER [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							RX_WD [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_TRIGGER	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	TX_NOT_FULL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
4	TX_EMPTY	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
5	TX_OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
6	TX_UNDERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	TX_WD	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
16	RX_TRIGGER	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
18	RX_NOT_EMPTY	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
19	RX_FULL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
21	RX_OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
22	RX_UNDERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
24	RX_WD	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

17.4.19 I2S_INTR_MASK

Description: Interrupt mask register
Address: 0x40800F08
Offset: 0xF08
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	TX_UNDERFLOW [6:6]	TX_OVERFLOW [5:5]	TX_EMPTY [4:4]	None [3:2]		TX_NOT_FULL [1:1]	TX_TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							TX_WD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	RX_UNDERFLOW [22:22]	RX_OVERFLOW [21:21]	None [20:20]	RX_FULL [19:19]	RX_NOT_EMPTY [18:18]	None [17:17]	RX_TRIGGER [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							RX_WD [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_TRIGGER	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	TX_NOT_FULL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
4	TX_EMPTY	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
5	TX_OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
6	TX_UNDERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	TX_WD	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
16	RX_TRIGGER	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
18	RX_NOT_EMPTY	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
19	RX_FULL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
21	RX_OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
22	RX_UNDERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
24	RX_WD	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

17.4.20 I2S_INTR_MASKED

Description: Interrupt masked register
Address: 0x40800F0C
Offset: 0xF0C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	TX_UNDERFLOW [6:6]	TX_OVERFLOW [5:5]	TX_EMPTY [4:4]	None [3:2]		TX_NOT_FULL [1:1]	TX_TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							TX_WD [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	RX_UNDERFLOW [22:22]	RX_OVERFLOW [21:21]	None [20:20]	RX_FULL [19:19]	RX_NOT_EMPTY [18:18]	None [17:17]	RX_TRIGGER [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							RX_WD [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TX_TRIGGER	R	R	0	Logical and of corresponding request and mask bits.
1	TX_NOT_FULL	R	R	0	Logical and of corresponding request and mask bits.
4	TX_EMPTY	R	R	0	Logical and of corresponding request and mask bits.
5	TX_OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
6	TX_UNDERFLOW	R	R	0	Logical and of corresponding request and mask bits.
8	TX_WD	R	R	0	Logical and of corresponding request and mask bits.
16	RX_TRIGGER	R	R	0	Logical and of corresponding request and mask bits.
18	RX_NOT_EMPTY	R	R	0	Logical and of corresponding request and mask bits.
19	RX_FULL	R	R	0	Logical and of corresponding request and mask bits.
21	RX_OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
22	RX_UNDERFLOW	R	R	0	Logical and of corresponding request and mask bits.
24	RX_WD	R	R	0	Logical and of corresponding request and mask bits.

18 IPC

Description	IPC
Base Address	0x40220000
Size	0x10000
Slave Num	MMIO2 - 2

18.1 STRUCT 0

Register Name	Address	Permission	Description
IPC_STRUCT0_ACQUIRE	0x40220000	FULL	IPC acquire
IPC_STRUCT0_RELEASE	0x40220004	FULL	IPC release
IPC_STRUCT0_NOTIFY	0x40220008	FULL	IPC notification
IPC_STRUCT0_DATA0	0x4022000C	FULL	IPC data 0
IPC_STRUCT0_DATA1	0x40220010	FULL	IPC data 1
IPC_STRUCT0_LOCK_STATUS	0x4022001C	FULL	IPC lock status

18.2 STRUCT 1

Register Name	Address	Permission	Description
IPC_STRUCT1_ACQUIRE	0x40220020	FULL	IPC acquire
IPC_STRUCT1_RELEASE	0x40220024	FULL	IPC release
IPC_STRUCT1_NOTIFY	0x40220028	FULL	IPC notification
IPC_STRUCT1_DATA0	0x4022002C	FULL	IPC data 0
IPC_STRUCT1_DATA1	0x40220030	FULL	IPC data 1
IPC_STRUCT1_LOCK_STATUS	0x4022003C	FULL	IPC lock status

18.3 STRUCT 2

Register Name	Address	Permission	Description
IPC_STRUCT2_ACQUIRE	0x40220040	FULL	IPC acquire
IPC_STRUCT2_RELEASE	0x40220044	FULL	IPC release
IPC_STRUCT2_NOTIFY	0x40220048	FULL	IPC notification
IPC_STRUCT2_DATA0	0x4022004C	FULL	IPC data 0
IPC_STRUCT2_DATA1	0x40220050	FULL	IPC data 1
IPC_STRUCT2_LOCK_STATUS	0x4022005C	FULL	IPC lock status

18.4 STRUCT 3

Register Name	Address	Permission	Description
IPC_STRUCT3_ACQUIRE	0x40220060	FULL	IPC acquire
IPC_STRUCT3_RELEASE	0x40220064	FULL	IPC release
IPC_STRUCT3_NOTIFY	0x40220068	FULL	IPC notification
IPC_STRUCT3_DATA0	0x4022006C	FULL	IPC data 0
IPC_STRUCT3_DATA1	0x40220070	FULL	IPC data 1
IPC_STRUCT3_LOCK_STATUS	0x4022007C	FULL	IPC lock status

18.5 STRUCT 4

Register Name	Address	Permission	Description
IPC_STRUCT4_ACQUIRE	0x40220080	FULL	IPC acquire
IPC_STRUCT4_RELEASE	0x40220084	FULL	IPC release
IPC_STRUCT4_NOTIFY	0x40220088	FULL	IPC notification
IPC_STRUCT4_DATA0	0x4022008C	FULL	IPC data 0
IPC_STRUCT4_DATA1	0x40220090	FULL	IPC data 1
IPC_STRUCT4_LOCK_STATUS	0x4022009C	FULL	IPC lock status

18.6 STRUCT 5

Register Name	Address	Permission	Description
IPC_STRUCT5_ACQUIRE	0x402200A0	FULL	IPC acquire
IPC_STRUCT5_RELEASE	0x402200A4	FULL	IPC release
IPC_STRUCT5_NOTIFY	0x402200A8	FULL	IPC notification
IPC_STRUCT5_DATA0	0x402200AC	FULL	IPC data 0
IPC_STRUCT5_DATA1	0x402200B0	FULL	IPC data 1

Register Name	Address	Permission	Description
IPC_STRUCT5_LOCK_STATUS	0x402200BC	FULL	IPC lock status

18.7 STRUCT 6

Register Name	Address	Permission	Description
IPC_STRUCT6_ACQUIRE	0x402200C0	FULL	IPC acquire
IPC_STRUCT6_RELEASE	0x402200C4	FULL	IPC release
IPC_STRUCT6_NOTIFY	0x402200C8	FULL	IPC notification
IPC_STRUCT6_DATA0	0x402200CC	FULL	IPC data 0
IPC_STRUCT6_DATA1	0x402200D0	FULL	IPC data 1
IPC_STRUCT6_LOCK_STATUS	0x402200DC	FULL	IPC lock status

18.8 STRUCT 7

Register Name	Address	Permission	Description
IPC_STRUCT7_ACQUIRE	0x402200E0	FULL	IPC acquire
IPC_STRUCT7_RELEASE	0x402200E4	FULL	IPC release
IPC_STRUCT7_NOTIFY	0x402200E8	FULL	IPC notification
IPC_STRUCT7_DATA0	0x402200EC	FULL	IPC data 0
IPC_STRUCT7_DATA1	0x402200F0	FULL	IPC data 1
IPC_STRUCT7_LOCK_STATUS	0x402200FC	FULL	IPC lock status

18.9 INTR_STRUCT 0

Register Name	Address	Permission	Description
IPC_INTR_STRUCT0_INTR	0x40221000	FULL	Interrupt
IPC_INTR_STRUCT0_INTR_SET	0x40221004	FULL	Interrupt set
IPC_INTR_STRUCT0_INTR_MASK	0x40221008	FULL	Interrupt mask
IPC_INTR_STRUCT0_INTR_MASKED	0x4022100C	FULL	Interrupt masked

18.10 INTR_STRUCT 1

Register Name	Address	Permission	Description
IPC_INTR_STRUCT1_INTR	0x40221020	FULL	Interrupt
IPC_INTR_STRUCT1_INTR_SET	0x40221024	FULL	Interrupt set
IPC_INTR_STRUCT1_INTR_MASK	0x40221028	FULL	Interrupt mask
IPC_INTR_STRUCT1_INTR_MASKED	0x4022102C	FULL	Interrupt masked

18.11 INTR_STRUCT 2

Register Name	Address	Permission	Description
IPC_INTR_STRUCT2_INTR	0x40221040	FULL	Interrupt
IPC_INTR_STRUCT2_INTR_SET	0x40221044	FULL	Interrupt set
IPC_INTR_STRUCT2_INTR_MASK	0x40221048	FULL	Interrupt mask
IPC_INTR_STRUCT2_INTR_MASKED	0x4022104C	FULL	Interrupt masked

18.12 INTR_STRUCT 3

Register Name	Address	Permission	Description
IPC_INTR_STRUCT3_INTR	0x40221060	FULL	Interrupt
IPC_INTR_STRUCT3_INTR_SET	0x40221064	FULL	Interrupt set
IPC_INTR_STRUCT3_INTR_MASK	0x40221068	FULL	Interrupt mask
IPC_INTR_STRUCT3_INTR_MASKED	0x4022106C	FULL	Interrupt masked

18.13 INTR_STRUCT 4

Register Name	Address	Permission	Description
IPC_INTR_STRUCT4_INTR	0x40221080	FULL	Interrupt
IPC_INTR_STRUCT4_INTR_SET	0x40221084	FULL	Interrupt set
IPC_INTR_STRUCT4_INTR_MASK	0x40221088	FULL	Interrupt mask
IPC_INTR_STRUCT4_INTR_MASKED	0x4022108C	FULL	Interrupt masked

18.14 INTR_STRUCT 5

Register Name	Address	Permission	Description
IPC_INTR_STRUCT5_INTR	0x402210A0	FULL	Interrupt
IPC_INTR_STRUCT5_INTR_SET	0x402210A4	FULL	Interrupt set

Register Name	Address	Permission	Description
IPC_INTR_STRUCT5_INTR_MASK	0x402210A8	FULL	Interrupt mask
IPC_INTR_STRUCT5_INTR_MASKED	0x402210AC	FULL	Interrupt masked

18.15 INTR_STRUCT 6

Register Name	Address	Permission	Description
IPC_INTR_STRUCT6_INTR	0x402210C0	FULL	Interrupt
IPC_INTR_STRUCT6_INTR_SET	0x402210C4	FULL	Interrupt set
IPC_INTR_STRUCT6_INTR_MASK	0x402210C8	FULL	Interrupt mask
IPC_INTR_STRUCT6_INTR_MASKED	0x402210CC	FULL	Interrupt masked

18.16 INTR_STRUCT 7

Register Name	Address	Permission	Description
IPC_INTR_STRUCT7_INTR	0x402210E0	FULL	Interrupt
IPC_INTR_STRUCT7_INTR_SET	0x402210E4	FULL	Interrupt set
IPC_INTR_STRUCT7_INTR_MASK	0x402210E8	FULL	Interrupt mask
IPC_INTR_STRUCT7_INTR_MASKED	0x402210EC	FULL	Interrupt masked

18.17 Register Details

18.17.1 STRUCT

18.17.1.1 IPC_STRUCT_ACQUIRE

Description: IPC acquire
Address: 0x40220000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register is used to acquire a lock.

A non test controller (the master identifier of the access is NOT '15') read access attempts to acquire a lock. This read access will return the result of the attempt as well as parameters of the master which successfully acquired the lock.

A test controller (the master identifier of the access is '15') read access returns value of LOCK_STATUS. A test controller write access attempts to acquire a lock (the write data value is ignored and does not matter). A separate LOCK_STATUS read access is required to return the result of the attempt.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:2]		NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				MS [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	SUCCESS [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	R	R	Undefined	User/privileged access control: '0': user mode. '1': privileged mode. This field is set with the user/privileged access control of the access that successfully acquired the lock.
1	NS	R	R	Undefined	Secure/non-secure access control: '0': secure. '1': non-secure. This field is set with the secure/non-secure access control of the access that successfully acquired the lock.
4:7	PC	R	R	Undefined	This field specifies the protection context that successfully acquired the lock.
8:11	MS	R	R	Undefined	This field specifies the bus master identifier that successfully acquired the lock.

Bits	Name	SW	HW	Default or Enum	Description
31	SUCCESS	R	R	0	Specifies if the lock is successfully acquired or not (reading the ACQUIRE register can have affect on SUCCESS and LOCK_STATUS.ACQUIRED): '0': Not successfully acquired; i.e. the lock was already acquired by another read transaction and not released. The P, NS, PC and MS fields reflect the access attributes of the transaction that previously successfully acuiRED the lock; the fields are NOT affected by the current access. '1': Successfully acquired. The P, NS, PC and MS fields reflect the access attributes of the current access. Note that this field is NOT SW writable. A lock is released by writing to the associated RELEASE register (irrespective of the write value).

18.17.1.2 IPC_STRUCT_RELEASE

Description: IPC release
Address: 0x40220004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: This register is used to release a lock.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INTR_RELEASE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INTR_RELEASE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	INTR_RELEASE	W	W	0	Writing this field releases a lock and allows for the generation of release events to the IPC interrupt structures, but only when the lock is acquired (LOCK_STATUS.ACQUIRED is '1'). The IPC release cause fields associated with this IPC structure are set to '1', but only for those IPC interrupt structures for which the corresponding bit field in INTR_RELEASE[] is set to '1'. SW writes a '1' to the bit fields to generate a release event. Due to the transient nature of this event, SW always reads a '0' from this field.

18.17.1.3 IPC_STRUCT_NOTIFY

Description: IPC notification
Address: 0x40220008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INTR_NOTIFY [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INTR_NOTIFY [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	INTR_NOTIFY	W	W	0	This field allows for the generation of notification events to the IPC interrupt structures. The IPC notification cause fields associated with this IPC structure are set to '1', but only for those IPC interrupt structures for which the corresponding bit field in INTR_NOTIFY[] is set to '1'. SW writes a '1' to the bit fields to generate a notify event. Due to the transient nature of this event, SW always reads a '0' from this field.

18.17.1.4 IPC_STRUCT_DATA0

Description: IPC data 0
Address: 0x4022000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	Undefined	This field holds a 32-bit data element that is associated with the IPC structure.

18.17.1.5 IPC_STRUCT_DATA1

Description: IPC data 1
Address: 0x40220010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	RW	RW	Undefined	This field holds a 32-bit data element that is associated with the IPC structure.

18.17.1.6 IPC_STRUCT_LOCK_STATUS

Description: IPC lock status
Address: 0x4022001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PC [7:4]				None [3:2]		NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				MS [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ACQUIRED [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	R	R	Undefined	This field specifies the user/privileged access control: '0': user mode. '1': privileged mode.
1	NS	R	R	Undefined	This field specifies the secure/non-secure access control: '0': secure. '1': non-secure.
4:7	PC	R	R	Undefined	This field specifies the protection context that successfully acquired the lock.
8:11	MS	R	R	Undefined	This field specifies the bus master identifier that successfully acquired the lock.
31	ACQUIRED	R	R	0	Specifies if the lock is acquired. This field is set to '1', if a ACQUIRE read transfer successfully acquires the lock (the ACQUIRE read transfer returns ACQUIRE.SUCCESS as '1'). If zero, P, NS, PC, and MS are not valid.

18.17.2 INTR_STRUCT

18.17.2.1 IPC_INTR_STRUCT_INTR

Description: Interrupt
Address: 0x40221000
Offset: 0x0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RELEASE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RELEASE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	NOTIFY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	NOTIFY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RELEASE	RW1C	RW1C	0	These interrupt cause fields are activated (HW sets the field to '1') when a IPC release event is detected. One bit field for each master. SW writes a '1' to these field to clear the interrupt cause.
16:31	NOTIFY	RW1C	RW1C	0	These interrupt cause fields are activated (HW sets the field to '1') when a IPC notification event is detected. One bit field for each master. SW writes a '1' to these field to clear the interrupt cause.

18.17.2.2 IPC_INTR_STRUCT_INTR_SET

Description: Interrupt set
Address: 0x40221004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the INTR register. For debug purposes, SW can write a '1' to activate a specific interrupt cause (this allows for debug of the SW ISR, without relying on HW to activate the interrupt cause).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RELEASE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	RELEASE [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	NOTIFY [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	NOTIFY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RELEASE	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in the INTR register.
16:31	NOTIFY	RW1S	RW1S	0	SW writes a '1' to this field to set the corresponding field in the INTR register.

18.17.2.3 IPC_INTR_STRUCT_INTR_MASK

Description: Interrupt mask
Address: 0x40221008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RELEASE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RELEASE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	NOTIFY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	NOTIFY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RELEASE	RW	RW	0	Mask bit for corresponding field in the INTR register.
16:31	NOTIFY	RW	RW	0	Mask bit for corresponding field in the INTR register.

18.17.2.4 IPC_INTR_STRUCT_INTR_MASKED

Description: Interrupt masked
Address: 0x4022100C
Offset: 0xC
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects 'a bitwise AND' between the INTR and INTR_MASK registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RELEASE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RELEASE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	NOTIFY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	NOTIFY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RELEASE	R	R	0	Logical and of corresponding request and mask bits.
16:31	NOTIFY	R	R	0	Logical and of corresponding INTR and INTR_MASK fields.

19 PASS

Description	Programmable Analog Subsystem for S40E
Base Address	0x40900000
Size	0x100000
Slave Num	MMIO9 - 0

19.1 SAR 0

Register Name	Address	Permission	Description
PASS0_SAR0_CTL	0x40900000	FULL	Analog control register.
PASS0_SAR0_DIAG_CTL	0x40900004	FULL	Diagnostic Reference control register.
PASS0_SAR0_PRECOND_CTL	0x40900010	FULL	Preconditioning control register.
PASS0_SAR0_ANA_CAL	0x40900080	FULL	Current analog calibration values
PASS0_SAR0_DIG_CAL	0x40900084	FULL	Current digital calibration values
PASS0_SAR0_ANA_CAL_ALT	0x40900090	FULL	Alternate analog calibration values
PASS0_SAR0_DIG_CAL_ALT	0x40900094	FULL	Alternate digital calibration values
PASS0_SAR0_CAL_UPD_CMD	0x40900098	FULL	Calibration update command
PASS0_SAR0_TR_PEND	0x40900100	FULL	Trigger pending status
PASS0_SAR0_WORK_VALID	0x40900180	FULL	Channel working data register 'valid' bits
PASS0_SAR0_WORK_RANGE	0x40900184	FULL	Range detected
PASS0_SAR0_WORK_RANGE_HI	0x40900188	FULL	Range detect above Hi flag
PASS0_SAR0_WORK_PULSE	0x4090018C	FULL	Pulse detected
PASS0_SAR0_RESULT_VALID	0x409001A0	FULL	Channel result data register 'valid' bits
PASS0_SAR0_RESULT_RANGE_HI	0x409001A4	FULL	Channel Range above Hi flags
PASS0_SAR0_STATUS	0x40900200	FULL	Current status of internal SAR registers (mostly for debug)
PASS0_SAR0_AVG_STAT	0x40900204	FULL	Current averaging status (for debug)

19.1.1 CH 0

Register Name	Address	Permission	Description
PASS0_SAR0_CH0_TR_CTL	0x40900800	FULL	Trigger control.
PASS0_SAR0_CH0_SAMPLE_CTL	0x40900804	FULL	Sample control.
PASS0_SAR0_CH0_POST_CTL	0x40900808	FULL	Post processing control
PASS0_SAR0_CH0_RANGE_CTL	0x4090080C	FULL	Range thresholds
PASS0_SAR0_CH0_INTR	0x40900810	FULL	Interrupt request register.
PASS0_SAR0_CH0_INTR_SET	0x40900814	FULL	Interrupt set request register
PASS0_SAR0_CH0_INTR_MASK	0x40900818	FULL	Interrupt mask register.
PASS0_SAR0_CH0_INTR_MASKED	0x4090081C	FULL	Interrupt masked request register
PASS0_SAR0_CH0_WORK	0x40900820	FULL	Working data register
PASS0_SAR0_CH0_RESULT	0x40900824	FULL	Result data register
PASS0_SAR0_CH0_GRP_STAT	0x40900828	FULL	Group status register
PASS0_SAR0_CH0_ENABLE	0x40900838	FULL	Enable register
PASS0_SAR0_CH0_TR_CMD	0x4090083C	FULL	Software triggers

19.1.2 CH 1

Register Name	Address	Permission	Description
PASS0_SAR0_CH1_TR_CTL	0x40900840	FULL	Trigger control.
PASS0_SAR0_CH1_SAMPLE_CTL	0x40900844	FULL	Sample control.
PASS0_SAR0_CH1_POST_CTL	0x40900848	FULL	Post processing control
PASS0_SAR0_CH1_RANGE_CTL	0x4090084C	FULL	Range thresholds
PASS0_SAR0_CH1_INTR	0x40900850	FULL	Interrupt request register.
PASS0_SAR0_CH1_INTR_SET	0x40900854	FULL	Interrupt set request register
PASS0_SAR0_CH1_INTR_MASK	0x40900858	FULL	Interrupt mask register.
PASS0_SAR0_CH1_INTR_MASKED	0x4090085C	FULL	Interrupt masked request register
PASS0_SAR0_CH1_WORK	0x40900860	FULL	Working data register
PASS0_SAR0_CH1_RESULT	0x40900864	FULL	Result data register
PASS0_SAR0_CH1_GRP_STAT	0x40900868	FULL	Group status register
PASS0_SAR0_CH1_ENABLE	0x40900878	FULL	Enable register
PASS0_SAR0_CH1_TR_CMD	0x4090087C	FULL	Software triggers

19.1.3 CH 2

Register Name	Address	Permission	Description
PASS0_SAR0_CH2_TR_CTL	0x40900880	FULL	Trigger control.
PASS0_SAR0_CH2_SAMPLE_CTL	0x40900884	FULL	Sample control.
PASS0_SAR0_CH2_POST_CTL	0x40900888	FULL	Post processing control
PASS0_SAR0_CH2_RANGE_CTL	0x4090088C	FULL	Range thresholds
PASS0_SAR0_CH2_INTR	0x40900890	FULL	Interrupt request register.
PASS0_SAR0_CH2_INTR_SET	0x40900894	FULL	Interrupt set request register
PASS0_SAR0_CH2_INTR_MASK	0x40900898	FULL	Interrupt mask register.
PASS0_SAR0_CH2_INTR_MASKED	0x4090089C	FULL	Interrupt masked request register
PASS0_SAR0_CH2_WORK	0x409008A0	FULL	Working data register
PASS0_SAR0_CH2_RESULT	0x409008A4	FULL	Result data register
PASS0_SAR0_CH2_GRP_STAT	0x409008A8	FULL	Group status register
PASS0_SAR0_CH2_ENABLE	0x409008B8	FULL	Enable register
PASS0_SAR0_CH2_TR_CMD	0x409008BC	FULL	Software triggers

19.1.4 CH 3

Register Name	Address	Permission	Description
PASS0_SAR0_CH3_TR_CTL	0x409008C0	FULL	Trigger control.
PASS0_SAR0_CH3_SAMPLE_CTL	0x409008C4	FULL	Sample control.
PASS0_SAR0_CH3_POST_CTL	0x409008C8	FULL	Post processing control
PASS0_SAR0_CH3_RANGE_CTL	0x409008CC	FULL	Range thresholds
PASS0_SAR0_CH3_INTR	0x409008D0	FULL	Interrupt request register.
PASS0_SAR0_CH3_INTR_SET	0x409008D4	FULL	Interrupt set request register
PASS0_SAR0_CH3_INTR_MASK	0x409008D8	FULL	Interrupt mask register.
PASS0_SAR0_CH3_INTR_MASKED	0x409008DC	FULL	Interrupt masked request register
PASS0_SAR0_CH3_WORK	0x409008E0	FULL	Working data register
PASS0_SAR0_CH3_RESULT	0x409008E4	FULL	Result data register
PASS0_SAR0_CH3_GRP_STAT	0x409008E8	FULL	Group status register
PASS0_SAR0_CH3_ENABLE	0x409008F8	FULL	Enable register
PASS0_SAR0_CH3_TR_CMD	0x409008FC	FULL	Software triggers

19.1.5 CH 4

Register Name	Address	Permission	Description
PASS0_SAR0_CH4_TR_CTL	0x40900900	FULL	Trigger control.
PASS0_SAR0_CH4_SAMPLE_CTL	0x40900904	FULL	Sample control.
PASS0_SAR0_CH4_POST_CTL	0x40900908	FULL	Post processing control
PASS0_SAR0_CH4_RANGE_CTL	0x4090090C	FULL	Range thresholds
PASS0_SAR0_CH4_INTR	0x40900910	FULL	Interrupt request register.
PASS0_SAR0_CH4_INTR_SET	0x40900914	FULL	Interrupt set request register
PASS0_SAR0_CH4_INTR_MASK	0x40900918	FULL	Interrupt mask register.
PASS0_SAR0_CH4_INTR_MASKED	0x4090091C	FULL	Interrupt masked request register
PASS0_SAR0_CH4_WORK	0x40900920	FULL	Working data register
PASS0_SAR0_CH4_RESULT	0x40900924	FULL	Result data register
PASS0_SAR0_CH4_GRP_STAT	0x40900928	FULL	Group status register
PASS0_SAR0_CH4_ENABLE	0x40900938	FULL	Enable register
PASS0_SAR0_CH4_TR_CMD	0x4090093C	FULL	Software triggers

19.1.6 CH 5

Register Name	Address	Permission	Description
PASS0_SAR0_CH5_TR_CTL	0x40900940	FULL	Trigger control.
PASS0_SAR0_CH5_SAMPLE_CTL	0x40900944	FULL	Sample control.
PASS0_SAR0_CH5_POST_CTL	0x40900948	FULL	Post processing control
PASS0_SAR0_CH5_RANGE_CTL	0x4090094C	FULL	Range thresholds
PASS0_SAR0_CH5_INTR	0x40900950	FULL	Interrupt request register.
PASS0_SAR0_CH5_INTR_SET	0x40900954	FULL	Interrupt set request register
PASS0_SAR0_CH5_INTR_MASK	0x40900958	FULL	Interrupt mask register.
PASS0_SAR0_CH5_INTR_MASKED	0x4090095C	FULL	Interrupt masked request register
PASS0_SAR0_CH5_WORK	0x40900960	FULL	Working data register
PASS0_SAR0_CH5_RESULT	0x40900964	FULL	Result data register
PASS0_SAR0_CH5_GRP_STAT	0x40900968	FULL	Group status register
PASS0_SAR0_CH5_ENABLE	0x40900978	FULL	Enable register
PASS0_SAR0_CH5_TR_CMD	0x4090097C	FULL	Software triggers

19.1.7 CH 6

Register Name	Address	Permission	Description
PASS0_SAR0_CH6_TR_CTL	0x40900980	FULL	Trigger control.
PASS0_SAR0_CH6_SAMPLE_CTL	0x40900984	FULL	Sample control.
PASS0_SAR0_CH6_POST_CTL	0x40900988	FULL	Post processing control
PASS0_SAR0_CH6_RANGE_CTL	0x4090098C	FULL	Range thresholds
PASS0_SAR0_CH6_INTR	0x40900990	FULL	Interrupt request register.
PASS0_SAR0_CH6_INTR_SET	0x40900994	FULL	Interrupt set request register
PASS0_SAR0_CH6_INTR_MASK	0x40900998	FULL	Interrupt mask register.
PASS0_SAR0_CH6_INTR_MASKED	0x4090099C	FULL	Interrupt masked request register
PASS0_SAR0_CH6_WORK	0x409009A0	FULL	Working data register
PASS0_SAR0_CH6_RESULT	0x409009A4	FULL	Result data register
PASS0_SAR0_CH6_GRP_STAT	0x409009A8	FULL	Group status register
PASS0_SAR0_CH6_ENABLE	0x409009B8	FULL	Enable register
PASS0_SAR0_CH6_TR_CMD	0x409009BC	FULL	Software triggers

19.1.8 CH 7

Register Name	Address	Permission	Description
PASS0_SAR0_CH7_TR_CTL	0x409009C0	FULL	Trigger control.
PASS0_SAR0_CH7_SAMPLE_CTL	0x409009C4	FULL	Sample control.
PASS0_SAR0_CH7_POST_CTL	0x409009C8	FULL	Post processing control
PASS0_SAR0_CH7_RANGE_CTL	0x409009CC	FULL	Range thresholds
PASS0_SAR0_CH7_INTR	0x409009D0	FULL	Interrupt request register.
PASS0_SAR0_CH7_INTR_SET	0x409009D4	FULL	Interrupt set request register
PASS0_SAR0_CH7_INTR_MASK	0x409009D8	FULL	Interrupt mask register.
PASS0_SAR0_CH7_INTR_MASKED	0x409009DC	FULL	Interrupt masked request register
PASS0_SAR0_CH7_WORK	0x409009E0	FULL	Working data register
PASS0_SAR0_CH7_RESULT	0x409009E4	FULL	Result data register
PASS0_SAR0_CH7_GRP_STAT	0x409009E8	FULL	Group status register
PASS0_SAR0_CH7_ENABLE	0x409009F8	FULL	Enable register
PASS0_SAR0_CH7_TR_CMD	0x409009FC	FULL	Software triggers

19.1.9 CH 8

Register Name	Address	Permission	Description
PASS0_SAR0_CH8_TR_CTL	0x40900A00	FULL	Trigger control.
PASS0_SAR0_CH8_SAMPLE_CTL	0x40900A04	FULL	Sample control.
PASS0_SAR0_CH8_POST_CTL	0x40900A08	FULL	Post processing control
PASS0_SAR0_CH8_RANGE_CTL	0x40900A0C	FULL	Range thresholds
PASS0_SAR0_CH8_INTR	0x40900A10	FULL	Interrupt request register.
PASS0_SAR0_CH8_INTR_SET	0x40900A14	FULL	Interrupt set request register
PASS0_SAR0_CH8_INTR_MASK	0x40900A18	FULL	Interrupt mask register.
PASS0_SAR0_CH8_INTR_MASKED	0x40900A1C	FULL	Interrupt masked request register
PASS0_SAR0_CH8_WORK	0x40900A20	FULL	Working data register
PASS0_SAR0_CH8_RESULT	0x40900A24	FULL	Result data register
PASS0_SAR0_CH8_GRP_STAT	0x40900A28	FULL	Group status register
PASS0_SAR0_CH8_ENABLE	0x40900A38	FULL	Enable register
PASS0_SAR0_CH8_TR_CMD	0x40900A3C	FULL	Software triggers

19.1.10 CH 9

Register Name	Address	Permission	Description
PASS0_SAR0_CH9_TR_CTL	0x40900A40	FULL	Trigger control.
PASS0_SAR0_CH9_SAMPLE_CTL	0x40900A44	FULL	Sample control.
PASS0_SAR0_CH9_POST_CTL	0x40900A48	FULL	Post processing control
PASS0_SAR0_CH9_RANGE_CTL	0x40900A4C	FULL	Range thresholds
PASS0_SAR0_CH9_INTR	0x40900A50	FULL	Interrupt request register.
PASS0_SAR0_CH9_INTR_SET	0x40900A54	FULL	Interrupt set request register
PASS0_SAR0_CH9_INTR_MASK	0x40900A58	FULL	Interrupt mask register.
PASS0_SAR0_CH9_INTR_MASKED	0x40900A5C	FULL	Interrupt masked request register
PASS0_SAR0_CH9_WORK	0x40900A60	FULL	Working data register
PASS0_SAR0_CH9_RESULT	0x40900A64	FULL	Result data register
PASS0_SAR0_CH9_GRP_STAT	0x40900A68	FULL	Group status register
PASS0_SAR0_CH9_ENABLE	0x40900A78	FULL	Enable register
PASS0_SAR0_CH9_TR_CMD	0x40900A7C	FULL	Software triggers

19.1.11 CH 10

Register Name	Address	Permission	Description
PASS0_SAR0_CH10_TR_CTL	0x40900A80	FULL	Trigger control.
PASS0_SAR0_CH10_SAMPLE_CTL	0x40900A84	FULL	Sample control.
PASS0_SAR0_CH10_POST_CTL	0x40900A88	FULL	Post processing control
PASS0_SAR0_CH10_RANGE_CTL	0x40900A8C	FULL	Range thresholds
PASS0_SAR0_CH10_INTR	0x40900A90	FULL	Interrupt request register.
PASS0_SAR0_CH10_INTR_SET	0x40900A94	FULL	Interrupt set request register
PASS0_SAR0_CH10_INTR_MASK	0x40900A98	FULL	Interrupt mask register.
PASS0_SAR0_CH10_INTR_MASKED	0x40900A9C	FULL	Interrupt masked request register
PASS0_SAR0_CH10_WORK	0x40900AA0	FULL	Working data register
PASS0_SAR0_CH10_RESULT	0x40900AA4	FULL	Result data register
PASS0_SAR0_CH10_GRP_STAT	0x40900AA8	FULL	Group status register
PASS0_SAR0_CH10_ENABLE	0x40900AB8	FULL	Enable register
PASS0_SAR0_CH10_TR_CMD	0x40900ABC	FULL	Software triggers

19.1.12 CH 11

Register Name	Address	Permission	Description
PASS0_SAR0_CH11_TR_CTL	0x40900AC0	FULL	Trigger control.
PASS0_SAR0_CH11_SAMPLE_CTL	0x40900AC4	FULL	Sample control.
PASS0_SAR0_CH11_POST_CTL	0x40900AC8	FULL	Post processing control
PASS0_SAR0_CH11_RANGE_CTL	0x40900ACC	FULL	Range thresholds
PASS0_SAR0_CH11_INTR	0x40900AD0	FULL	Interrupt request register.
PASS0_SAR0_CH11_INTR_SET	0x40900AD4	FULL	Interrupt set request register
PASS0_SAR0_CH11_INTR_MASK	0x40900AD8	FULL	Interrupt mask register.
PASS0_SAR0_CH11_INTR_MASKED	0x40900ADC	FULL	Interrupt masked request register
PASS0_SAR0_CH11_WORK	0x40900AE0	FULL	Working data register
PASS0_SAR0_CH11_RESULT	0x40900AE4	FULL	Result data register
PASS0_SAR0_CH11_GRP_STAT	0x40900AE8	FULL	Group status register
PASS0_SAR0_CH11_ENABLE	0x40900AF8	FULL	Enable register
PASS0_SAR0_CH11_TR_CMD	0x40900AFC	FULL	Software triggers

19.1.13 CH 12

Register Name	Address	Permission	Description
PASS0_SAR0_CH12_TR_CTL	0x40900B00	FULL	Trigger control.
PASS0_SAR0_CH12_SAMPLE_CTL	0x40900B04	FULL	Sample control.
PASS0_SAR0_CH12_POST_CTL	0x40900B08	FULL	Post processing control
PASS0_SAR0_CH12_RANGE_CTL	0x40900B0C	FULL	Range thresholds
PASS0_SAR0_CH12_INTR	0x40900B10	FULL	Interrupt request register.
PASS0_SAR0_CH12_INTR_SET	0x40900B14	FULL	Interrupt set request register
PASS0_SAR0_CH12_INTR_MASK	0x40900B18	FULL	Interrupt mask register.
PASS0_SAR0_CH12_INTR_MASKED	0x40900B1C	FULL	Interrupt masked request register
PASS0_SAR0_CH12_WORK	0x40900B20	FULL	Working data register
PASS0_SAR0_CH12_RESULT	0x40900B24	FULL	Result data register
PASS0_SAR0_CH12_GRP_STAT	0x40900B28	FULL	Group status register
PASS0_SAR0_CH12_ENABLE	0x40900B38	FULL	Enable register
PASS0_SAR0_CH12_TR_CMD	0x40900B3C	FULL	Software triggers

19.1.14 CH 13

Register Name	Address	Permission	Description
PASS0_SAR0_CH13_TR_CTL	0x40900B40	FULL	Trigger control.
PASS0_SAR0_CH13_SAMPLE_CTL	0x40900B44	FULL	Sample control.
PASS0_SAR0_CH13_POST_CTL	0x40900B48	FULL	Post processing control
PASS0_SAR0_CH13_RANGE_CTL	0x40900B4C	FULL	Range thresholds
PASS0_SAR0_CH13_INTR	0x40900B50	FULL	Interrupt request register.
PASS0_SAR0_CH13_INTR_SET	0x40900B54	FULL	Interrupt set request register
PASS0_SAR0_CH13_INTR_MASK	0x40900B58	FULL	Interrupt mask register.
PASS0_SAR0_CH13_INTR_MASKED	0x40900B5C	FULL	Interrupt masked request register
PASS0_SAR0_CH13_WORK	0x40900B60	FULL	Working data register
PASS0_SAR0_CH13_RESULT	0x40900B64	FULL	Result data register
PASS0_SAR0_CH13_GRP_STAT	0x40900B68	FULL	Group status register
PASS0_SAR0_CH13_ENABLE	0x40900B78	FULL	Enable register
PASS0_SAR0_CH13_TR_CMD	0x40900B7C	FULL	Software triggers

19.1.15 CH 14

Register Name	Address	Permission	Description
PASS0_SAR0_CH14_TR_CTL	0x40900B80	FULL	Trigger control.
PASS0_SAR0_CH14_SAMPLE_CTL	0x40900B84	FULL	Sample control.
PASS0_SAR0_CH14_POST_CTL	0x40900B88	FULL	Post processing control
PASS0_SAR0_CH14_RANGE_CTL	0x40900B8C	FULL	Range thresholds
PASS0_SAR0_CH14_INTR	0x40900B90	FULL	Interrupt request register.
PASS0_SAR0_CH14_INTR_SET	0x40900B94	FULL	Interrupt set request register
PASS0_SAR0_CH14_INTR_MASK	0x40900B98	FULL	Interrupt mask register.
PASS0_SAR0_CH14_INTR_MASKED	0x40900B9C	FULL	Interrupt masked request register
PASS0_SAR0_CH14_WORK	0x40900BA0	FULL	Working data register
PASS0_SAR0_CH14_RESULT	0x40900BA4	FULL	Result data register
PASS0_SAR0_CH14_GRP_STAT	0x40900BA8	FULL	Group status register
PASS0_SAR0_CH14_ENABLE	0x40900BB8	FULL	Enable register
PASS0_SAR0_CH14_TR_CMD	0x40900BBC	FULL	Software triggers

19.1.16 CH 15

Register Name	Address	Permission	Description
PASS0_SAR0_CH15_TR_CTL	0x40900BC0	FULL	Trigger control.
PASS0_SAR0_CH15_SAMPLE_CTL	0x40900BC4	FULL	Sample control.
PASS0_SAR0_CH15_POST_CTL	0x40900BC8	FULL	Post processing control
PASS0_SAR0_CH15_RANGE_CTL	0x40900BCC	FULL	Range thresholds
PASS0_SAR0_CH15_INTR	0x40900BD0	FULL	Interrupt request register.
PASS0_SAR0_CH15_INTR_SET	0x40900BD4	FULL	Interrupt set request register
PASS0_SAR0_CH15_INTR_MASK	0x40900BD8	FULL	Interrupt mask register.
PASS0_SAR0_CH15_INTR_MASKED	0x40900BDC	FULL	Interrupt masked request register
PASS0_SAR0_CH15_WORK	0x40900BE0	FULL	Working data register
PASS0_SAR0_CH15_RESULT	0x40900BE4	FULL	Result data register
PASS0_SAR0_CH15_GRP_STAT	0x40900BE8	FULL	Group status register
PASS0_SAR0_CH15_ENABLE	0x40900BF8	FULL	Enable register
PASS0_SAR0_CH15_TR_CMD	0x40900BFC	FULL	Software triggers

19.1.17 CH 16

Register Name	Address	Permission	Description
PASS0_SAR0_CH16_TR_CTL	0x40900C00	FULL	Trigger control.
PASS0_SAR0_CH16_SAMPLE_CTL	0x40900C04	FULL	Sample control.
PASS0_SAR0_CH16_POST_CTL	0x40900C08	FULL	Post processing control
PASS0_SAR0_CH16_RANGE_CTL	0x40900C0C	FULL	Range thresholds
PASS0_SAR0_CH16_INTR	0x40900C10	FULL	Interrupt request register.
PASS0_SAR0_CH16_INTR_SET	0x40900C14	FULL	Interrupt set request register
PASS0_SAR0_CH16_INTR_MASK	0x40900C18	FULL	Interrupt mask register.
PASS0_SAR0_CH16_INTR_MASKED	0x40900C1C	FULL	Interrupt masked request register
PASS0_SAR0_CH16_WORK	0x40900C20	FULL	Working data register
PASS0_SAR0_CH16_RESULT	0x40900C24	FULL	Result data register
PASS0_SAR0_CH16_GRP_STAT	0x40900C28	FULL	Group status register
PASS0_SAR0_CH16_ENABLE	0x40900C38	FULL	Enable register
PASS0_SAR0_CH16_TR_CMD	0x40900C3C	FULL	Software triggers

19.1.18 CH 17

Register Name	Address	Permission	Description
PASS0_SAR0_CH17_TR_CTL	0x40900C40	FULL	Trigger control.
PASS0_SAR0_CH17_SAMPLE_CTL	0x40900C44	FULL	Sample control.
PASS0_SAR0_CH17_POST_CTL	0x40900C48	FULL	Post processing control
PASS0_SAR0_CH17_RANGE_CTL	0x40900C4C	FULL	Range thresholds
PASS0_SAR0_CH17_INTR	0x40900C50	FULL	Interrupt request register.
PASS0_SAR0_CH17_INTR_SET	0x40900C54	FULL	Interrupt set request register
PASS0_SAR0_CH17_INTR_MASK	0x40900C58	FULL	Interrupt mask register.
PASS0_SAR0_CH17_INTR_MASKED	0x40900C5C	FULL	Interrupt masked request register
PASS0_SAR0_CH17_WORK	0x40900C60	FULL	Working data register
PASS0_SAR0_CH17_RESULT	0x40900C64	FULL	Result data register
PASS0_SAR0_CH17_GRP_STAT	0x40900C68	FULL	Group status register
PASS0_SAR0_CH17_ENABLE	0x40900C78	FULL	Enable register
PASS0_SAR0_CH17_TR_CMD	0x40900C7C	FULL	Software triggers

19.1.19 CH 18

Register Name	Address	Permission	Description
PASS0_SAR0_CH18_TR_CTL	0x40900C80	FULL	Trigger control.
PASS0_SAR0_CH18_SAMPLE_CTL	0x40900C84	FULL	Sample control.
PASS0_SAR0_CH18_POST_CTL	0x40900C88	FULL	Post processing control
PASS0_SAR0_CH18_RANGE_CTL	0x40900C8C	FULL	Range thresholds
PASS0_SAR0_CH18_INTR	0x40900C90	FULL	Interrupt request register.
PASS0_SAR0_CH18_INTR_SET	0x40900C94	FULL	Interrupt set request register
PASS0_SAR0_CH18_INTR_MASK	0x40900C98	FULL	Interrupt mask register.
PASS0_SAR0_CH18_INTR_MASKED	0x40900C9C	FULL	Interrupt masked request register
PASS0_SAR0_CH18_WORK	0x40900CA0	FULL	Working data register
PASS0_SAR0_CH18_RESULT	0x40900CA4	FULL	Result data register
PASS0_SAR0_CH18_GRP_STAT	0x40900CA8	FULL	Group status register
PASS0_SAR0_CH18_ENABLE	0x40900CB8	FULL	Enable register
PASS0_SAR0_CH18_TR_CMD	0x40900CBC	FULL	Software triggers

19.1.20 CH 19

Register Name	Address	Permission	Description
PASS0_SAR0_CH19_TR_CTL	0x40900CC0	FULL	Trigger control.
PASS0_SAR0_CH19_SAMPLE_CTL	0x40900CC4	FULL	Sample control.
PASS0_SAR0_CH19_POST_CTL	0x40900CC8	FULL	Post processing control
PASS0_SAR0_CH19_RANGE_CTL	0x40900CCC	FULL	Range thresholds
PASS0_SAR0_CH19_INTR	0x40900CD0	FULL	Interrupt request register.
PASS0_SAR0_CH19_INTR_SET	0x40900CD4	FULL	Interrupt set request register
PASS0_SAR0_CH19_INTR_MASK	0x40900CD8	FULL	Interrupt mask register.
PASS0_SAR0_CH19_INTR_MASKED	0x40900CDC	FULL	Interrupt masked request register
PASS0_SAR0_CH19_WORK	0x40900CE0	FULL	Working data register
PASS0_SAR0_CH19_RESULT	0x40900CE4	FULL	Result data register
PASS0_SAR0_CH19_GRP_STAT	0x40900CE8	FULL	Group status register
PASS0_SAR0_CH19_ENABLE	0x40900CF8	FULL	Enable register
PASS0_SAR0_CH19_TR_CMD	0x40900CFC	FULL	Software triggers

19.1.21 CH 20

Register Name	Address	Permission	Description
PASS0_SAR0_CH20_TR_CTL	0x40900D00	FULL	Trigger control.
PASS0_SAR0_CH20_SAMPLE_CTL	0x40900D04	FULL	Sample control.
PASS0_SAR0_CH20_POST_CTL	0x40900D08	FULL	Post processing control
PASS0_SAR0_CH20_RANGE_CTL	0x40900D0C	FULL	Range thresholds
PASS0_SAR0_CH20_INTR	0x40900D10	FULL	Interrupt request register.
PASS0_SAR0_CH20_INTR_SET	0x40900D14	FULL	Interrupt set request register
PASS0_SAR0_CH20_INTR_MASK	0x40900D18	FULL	Interrupt mask register.
PASS0_SAR0_CH20_INTR_MASKED	0x40900D1C	FULL	Interrupt masked request register
PASS0_SAR0_CH20_WORK	0x40900D20	FULL	Working data register
PASS0_SAR0_CH20_RESULT	0x40900D24	FULL	Result data register
PASS0_SAR0_CH20_GRP_STAT	0x40900D28	FULL	Group status register
PASS0_SAR0_CH20_ENABLE	0x40900D38	FULL	Enable register
PASS0_SAR0_CH20_TR_CMD	0x40900D3C	FULL	Software triggers

19.1.22 CH 21

Register Name	Address	Permission	Description
PASS0_SAR0_CH21_TR_CTL	0x40900D40	FULL	Trigger control.
PASS0_SAR0_CH21_SAMPLE_CTL	0x40900D44	FULL	Sample control.
PASS0_SAR0_CH21_POST_CTL	0x40900D48	FULL	Post processing control
PASS0_SAR0_CH21_RANGE_CTL	0x40900D4C	FULL	Range thresholds
PASS0_SAR0_CH21_INTR	0x40900D50	FULL	Interrupt request register.
PASS0_SAR0_CH21_INTR_SET	0x40900D54	FULL	Interrupt set request register
PASS0_SAR0_CH21_INTR_MASK	0x40900D58	FULL	Interrupt mask register.
PASS0_SAR0_CH21_INTR_MASKED	0x40900D5C	FULL	Interrupt masked request register
PASS0_SAR0_CH21_WORK	0x40900D60	FULL	Working data register
PASS0_SAR0_CH21_RESULT	0x40900D64	FULL	Result data register
PASS0_SAR0_CH21_GRP_STAT	0x40900D68	FULL	Group status register
PASS0_SAR0_CH21_ENABLE	0x40900D78	FULL	Enable register
PASS0_SAR0_CH21_TR_CMD	0x40900D7C	FULL	Software triggers

19.1.23 CH 22

Register Name	Address	Permission	Description
PASS0_SAR0_CH22_TR_CTL	0x40900D80	FULL	Trigger control.
PASS0_SAR0_CH22_SAMPLE_CTL	0x40900D84	FULL	Sample control.
PASS0_SAR0_CH22_POST_CTL	0x40900D88	FULL	Post processing control
PASS0_SAR0_CH22_RANGE_CTL	0x40900D8C	FULL	Range thresholds
PASS0_SAR0_CH22_INTR	0x40900D90	FULL	Interrupt request register.
PASS0_SAR0_CH22_INTR_SET	0x40900D94	FULL	Interrupt set request register
PASS0_SAR0_CH22_INTR_MASK	0x40900D98	FULL	Interrupt mask register.
PASS0_SAR0_CH22_INTR_MASKED	0x40900D9C	FULL	Interrupt masked request register
PASS0_SAR0_CH22_WORK	0x40900DA0	FULL	Working data register
PASS0_SAR0_CH22_RESULT	0x40900DA4	FULL	Result data register
PASS0_SAR0_CH22_GRP_STAT	0x40900DA8	FULL	Group status register
PASS0_SAR0_CH22_ENABLE	0x40900DB8	FULL	Enable register
PASS0_SAR0_CH22_TR_CMD	0x40900DBC	FULL	Software triggers

19.1.24 CH 23

Register Name	Address	Permission	Description
PASS0_SAR0_CH23_TR_CTL	0x40900DC0	FULL	Trigger control.
PASS0_SAR0_CH23_SAMPLE_CTL	0x40900DC4	FULL	Sample control.
PASS0_SAR0_CH23_POST_CTL	0x40900DC8	FULL	Post processing control
PASS0_SAR0_CH23_RANGE_CTL	0x40900DCC	FULL	Range thresholds
PASS0_SAR0_CH23_INTR	0x40900DD0	FULL	Interrupt request register.
PASS0_SAR0_CH23_INTR_SET	0x40900DD4	FULL	Interrupt set request register
PASS0_SAR0_CH23_INTR_MASK	0x40900DD8	FULL	Interrupt mask register.
PASS0_SAR0_CH23_INTR_MASKED	0x40900DDC	FULL	Interrupt masked request register
PASS0_SAR0_CH23_WORK	0x40900DE0	FULL	Working data register
PASS0_SAR0_CH23_RESULT	0x40900DE4	FULL	Result data register
PASS0_SAR0_CH23_GRP_STAT	0x40900DE8	FULL	Group status register
PASS0_SAR0_CH23_ENABLE	0x40900DF8	FULL	Enable register
PASS0_SAR0_CH23_TR_CMD	0x40900DFC	FULL	Software triggers

19.1.25 CH 24

Register Name	Address	Permission	Description
PASS0_SAR0_CH24_TR_CTL	0x40900E00	FULL	Trigger control.
PASS0_SAR0_CH24_SAMPLE_CTL	0x40900E04	FULL	Sample control.
PASS0_SAR0_CH24_POST_CTL	0x40900E08	FULL	Post processing control
PASS0_SAR0_CH24_RANGE_CTL	0x40900E0C	FULL	Range thresholds
PASS0_SAR0_CH24_INTR	0x40900E10	FULL	Interrupt request register.
PASS0_SAR0_CH24_INTR_SET	0x40900E14	FULL	Interrupt set request register
PASS0_SAR0_CH24_INTR_MASK	0x40900E18	FULL	Interrupt mask register.
PASS0_SAR0_CH24_INTR_MASKED	0x40900E1C	FULL	Interrupt masked request register
PASS0_SAR0_CH24_WORK	0x40900E20	FULL	Working data register
PASS0_SAR0_CH24_RESULT	0x40900E24	FULL	Result data register
PASS0_SAR0_CH24_GRP_STAT	0x40900E28	FULL	Group status register
PASS0_SAR0_CH24_ENABLE	0x40900E38	FULL	Enable register
PASS0_SAR0_CH24_TR_CMD	0x40900E3C	FULL	Software triggers

19.1.26 CH 25

Register Name	Address	Permission	Description
PASS0_SAR0_CH25_TR_CTL	0x40900E40	FULL	Trigger control.
PASS0_SAR0_CH25_SAMPLE_CTL	0x40900E44	FULL	Sample control.
PASS0_SAR0_CH25_POST_CTL	0x40900E48	FULL	Post processing control
PASS0_SAR0_CH25_RANGE_CTL	0x40900E4C	FULL	Range thresholds
PASS0_SAR0_CH25_INTR	0x40900E50	FULL	Interrupt request register.
PASS0_SAR0_CH25_INTR_SET	0x40900E54	FULL	Interrupt set request register
PASS0_SAR0_CH25_INTR_MASK	0x40900E58	FULL	Interrupt mask register.
PASS0_SAR0_CH25_INTR_MASKED	0x40900E5C	FULL	Interrupt masked request register
PASS0_SAR0_CH25_WORK	0x40900E60	FULL	Working data register
PASS0_SAR0_CH25_RESULT	0x40900E64	FULL	Result data register
PASS0_SAR0_CH25_GRP_STAT	0x40900E68	FULL	Group status register
PASS0_SAR0_CH25_ENABLE	0x40900E78	FULL	Enable register
PASS0_SAR0_CH25_TR_CMD	0x40900E7C	FULL	Software triggers

19.1.27 CH 26

Register Name	Address	Permission	Description
PASS0_SAR0_CH26_TR_CTL	0x40900E80	FULL	Trigger control.
PASS0_SAR0_CH26_SAMPLE_CTL	0x40900E84	FULL	Sample control.
PASS0_SAR0_CH26_POST_CTL	0x40900E88	FULL	Post processing control
PASS0_SAR0_CH26_RANGE_CTL	0x40900E8C	FULL	Range thresholds
PASS0_SAR0_CH26_INTR	0x40900E90	FULL	Interrupt request register.
PASS0_SAR0_CH26_INTR_SET	0x40900E94	FULL	Interrupt set request register
PASS0_SAR0_CH26_INTR_MASK	0x40900E98	FULL	Interrupt mask register.
PASS0_SAR0_CH26_INTR_MASKED	0x40900E9C	FULL	Interrupt masked request register
PASS0_SAR0_CH26_WORK	0x40900EA0	FULL	Working data register
PASS0_SAR0_CH26_RESULT	0x40900EA4	FULL	Result data register
PASS0_SAR0_CH26_GRP_STAT	0x40900EA8	FULL	Group status register
PASS0_SAR0_CH26_ENABLE	0x40900EB8	FULL	Enable register
PASS0_SAR0_CH26_TR_CMD	0x40900EBC	FULL	Software triggers

19.1.28 CH 27

Register Name	Address	Permission	Description
PASS0_SAR0_CH27_TR_CTL	0x40900EC0	FULL	Trigger control.
PASS0_SAR0_CH27_SAMPLE_CTL	0x40900EC4	FULL	Sample control.
PASS0_SAR0_CH27_POST_CTL	0x40900EC8	FULL	Post processing control
PASS0_SAR0_CH27_RANGE_CTL	0x40900EC	FULL	Range thresholds
PASS0_SAR0_CH27_INTR	0x40900ED0	FULL	Interrupt request register.
PASS0_SAR0_CH27_INTR_SET	0x40900ED4	FULL	Interrupt set request register
PASS0_SAR0_CH27_INTR_MASK	0x40900ED8	FULL	Interrupt mask register.
PASS0_SAR0_CH27_INTR_MASKED	0x40900EDC	FULL	Interrupt masked request register
PASS0_SAR0_CH27_WORK	0x40900EE0	FULL	Working data register
PASS0_SAR0_CH27_RESULT	0x40900EE4	FULL	Result data register
PASS0_SAR0_CH27_GRP_STAT	0x40900EE8	FULL	Group status register
PASS0_SAR0_CH27_ENABLE	0x40900EF8	FULL	Enable register
PASS0_SAR0_CH27_TR_CMD	0x40900EFC	FULL	Software triggers

19.1.29 CH 28

Register Name	Address	Permission	Description
PASS0_SAR0_CH28_TR_CTL	0x40900F00	FULL	Trigger control.
PASS0_SAR0_CH28_SAMPLE_CTL	0x40900F04	FULL	Sample control.
PASS0_SAR0_CH28_POST_CTL	0x40900F08	FULL	Post processing control
PASS0_SAR0_CH28_RANGE_CTL	0x40900F0C	FULL	Range thresholds
PASS0_SAR0_CH28_INTR	0x40900F10	FULL	Interrupt request register.
PASS0_SAR0_CH28_INTR_SET	0x40900F14	FULL	Interrupt set request register
PASS0_SAR0_CH28_INTR_MASK	0x40900F18	FULL	Interrupt mask register.
PASS0_SAR0_CH28_INTR_MASKED	0x40900F1C	FULL	Interrupt masked request register
PASS0_SAR0_CH28_WORK	0x40900F20	FULL	Working data register
PASS0_SAR0_CH28_RESULT	0x40900F24	FULL	Result data register
PASS0_SAR0_CH28_GRP_STAT	0x40900F28	FULL	Group status register
PASS0_SAR0_CH28_ENABLE	0x40900F38	FULL	Enable register
PASS0_SAR0_CH28_TR_CMD	0x40900F3C	FULL	Software triggers

19.1.30 CH 29

Register Name	Address	Permission	Description
PASS0_SAR0_CH29_TR_CTL	0x40900F40	FULL	Trigger control.
PASS0_SAR0_CH29_SAMPLE_CTL	0x40900F44	FULL	Sample control.
PASS0_SAR0_CH29_POST_CTL	0x40900F48	FULL	Post processing control
PASS0_SAR0_CH29_RANGE_CTL	0x40900F4C	FULL	Range thresholds
PASS0_SAR0_CH29_INTR	0x40900F50	FULL	Interrupt request register.
PASS0_SAR0_CH29_INTR_SET	0x40900F54	FULL	Interrupt set request register
PASS0_SAR0_CH29_INTR_MASK	0x40900F58	FULL	Interrupt mask register.
PASS0_SAR0_CH29_INTR_MASKED	0x40900F5C	FULL	Interrupt masked request register
PASS0_SAR0_CH29_WORK	0x40900F60	FULL	Working data register
PASS0_SAR0_CH29_RESULT	0x40900F64	FULL	Result data register
PASS0_SAR0_CH29_GRP_STAT	0x40900F68	FULL	Group status register
PASS0_SAR0_CH29_ENABLE	0x40900F78	FULL	Enable register
PASS0_SAR0_CH29_TR_CMD	0x40900F7C	FULL	Software triggers

19.1.31 CH 30

Register Name	Address	Permission	Description
PASS0_SAR0_CH30_TR_CTL	0x40900F80	FULL	Trigger control.
PASS0_SAR0_CH30_SAMPLE_CTL	0x40900F84	FULL	Sample control.
PASS0_SAR0_CH30_POST_CTL	0x40900F88	FULL	Post processing control
PASS0_SAR0_CH30_RANGE_CTL	0x40900F8C	FULL	Range thresholds
PASS0_SAR0_CH30_INTR	0x40900F90	FULL	Interrupt request register.
PASS0_SAR0_CH30_INTR_SET	0x40900F94	FULL	Interrupt set request register
PASS0_SAR0_CH30_INTR_MASK	0x40900F98	FULL	Interrupt mask register.
PASS0_SAR0_CH30_INTR_MASKED	0x40900F9C	FULL	Interrupt masked request register
PASS0_SAR0_CH30_WORK	0x40900FA0	FULL	Working data register
PASS0_SAR0_CH30_RESULT	0x40900FA4	FULL	Result data register
PASS0_SAR0_CH30_GRP_STAT	0x40900FA8	FULL	Group status register
PASS0_SAR0_CH30_ENABLE	0x40900FB8	FULL	Enable register
PASS0_SAR0_CH30_TR_CMD	0x40900FBC	FULL	Software triggers

19.1.32 CH 31

Register Name	Address	Permission	Description
PASS0_SAR0_CH31_TR_CTL	0x40900FC0	FULL	Trigger control.
PASS0_SAR0_CH31_SAMPLE_CTL	0x40900FC4	FULL	Sample control.
PASS0_SAR0_CH31_POST_CTL	0x40900FC8	FULL	Post processing control
PASS0_SAR0_CH31_RANGE_CTL	0x40900FCC	FULL	Range thresholds
PASS0_SAR0_CH31_INTR	0x40900FD0	FULL	Interrupt request register.
PASS0_SAR0_CH31_INTR_SET	0x40900FD4	FULL	Interrupt set request register
PASS0_SAR0_CH31_INTR_MASK	0x40900FD8	FULL	Interrupt mask register.
PASS0_SAR0_CH31_INTR_MASKED	0x40900FDC	FULL	Interrupt masked request register
PASS0_SAR0_CH31_WORK	0x40900FE0	FULL	Working data register
PASS0_SAR0_CH31_RESULT	0x40900FE4	FULL	Result data register
PASS0_SAR0_CH31_GRP_STAT	0x40900FE8	FULL	Group status register
PASS0_SAR0_CH31_ENABLE	0x40900FF8	FULL	Enable register
PASS0_SAR0_CH31_TR_CMD	0x40900FFC	FULL	Software triggers

19.2 SAR 1

Register Name	Address	Permission	Description
PASS0_SAR1_CTL	0x40901000	FULL	Analog control register.
PASS0_SAR1_DIAG_CTL	0x40901004	FULL	Diagnostic Reference control register.
PASS0_SAR1_PRECOND_CTL	0x40901010	FULL	Preconditioning control register.
PASS0_SAR1_ANA_CAL	0x40901080	FULL	Current analog calibration values
PASS0_SAR1_DIG_CAL	0x40901084	FULL	Current digital calibration values
PASS0_SAR1_ANA_CAL_ALT	0x40901090	FULL	Alternate analog calibration values
PASS0_SAR1_DIG_CAL_ALT	0x40901094	FULL	Alternate digital calibration values
PASS0_SAR1_CAL_UPD_CMD	0x40901098	FULL	Calibration update command
PASS0_SAR1_TR_PEND	0x40901100	FULL	Trigger pending status
PASS0_SAR1_WORK_VALID	0x40901180	FULL	Channel working data register 'valid' bits
PASS0_SAR1_WORK_RANGE	0x40901184	FULL	Range detected
PASS0_SAR1_WORK_RANGE_HI	0x40901188	FULL	Range detect above Hi flag
PASS0_SAR1_WORK_PULSE	0x4090118C	FULL	Pulse detected
PASS0_SAR1_RESULT_VALID	0x409011A0	FULL	Channel result data register 'valid' bits
PASS0_SAR1_RESULT_RANGE_HI	0x409011A4	FULL	Channel Range above Hi flags
PASS0_SAR1_STATUS	0x40901200	FULL	Current status of internal SAR registers (mostly for debug)
PASS0_SAR1_AVG_STAT	0x40901204	FULL	Current averaging status (for debug)

19.2.1 CH 0

Register Name	Address	Permission	Description
PASS0_SAR1_CH0_TR_CTL	0x40901800	FULL	Trigger control.
PASS0_SAR1_CH0_SAMPLE_CTL	0x40901804	FULL	Sample control.
PASS0_SAR1_CH0_POST_CTL	0x40901808	FULL	Post processing control
PASS0_SAR1_CH0_RANGE_CTL	0x4090180C	FULL	Range thresholds
PASS0_SAR1_CH0_INTR	0x40901810	FULL	Interrupt request register.
PASS0_SAR1_CH0_INTR_SET	0x40901814	FULL	Interrupt set request register
PASS0_SAR1_CH0_INTR_MASK	0x40901818	FULL	Interrupt mask register.
PASS0_SAR1_CH0_INTR_MASKED	0x4090181C	FULL	Interrupt masked request register
PASS0_SAR1_CH0_WORK	0x40901820	FULL	Working data register

Register Name	Address	Permission	Description
PASS0_SAR1_CH0_RESULT	0x40901824	FULL	Result data register
PASS0_SAR1_CH0_GRP_STAT	0x40901828	FULL	Group status register
PASS0_SAR1_CH0_ENABLE	0x40901838	FULL	Enable register
PASS0_SAR1_CH0_TR_CMD	0x4090183C	FULL	Software triggers

19.2.2 CH 1

Register Name	Address	Permission	Description
PASS0_SAR1_CH1_TR_CTL	0x40901840	FULL	Trigger control.
PASS0_SAR1_CH1_SAMPLE_CTL	0x40901844	FULL	Sample control.
PASS0_SAR1_CH1_POST_CTL	0x40901848	FULL	Post processing control
PASS0_SAR1_CH1_RANGE_CTL	0x4090184C	FULL	Range thresholds
PASS0_SAR1_CH1_INTR	0x40901850	FULL	Interrupt request register.
PASS0_SAR1_CH1_INTR_SET	0x40901854	FULL	Interrupt set request register
PASS0_SAR1_CH1_INTR_MASK	0x40901858	FULL	Interrupt mask register.
PASS0_SAR1_CH1_INTR_MASKED	0x4090185C	FULL	Interrupt masked request register
PASS0_SAR1_CH1_WORK	0x40901860	FULL	Working data register
PASS0_SAR1_CH1_RESULT	0x40901864	FULL	Result data register
PASS0_SAR1_CH1_GRP_STAT	0x40901868	FULL	Group status register
PASS0_SAR1_CH1_ENABLE	0x40901878	FULL	Enable register
PASS0_SAR1_CH1_TR_CMD	0x4090187C	FULL	Software triggers

19.2.3 CH 2

Register Name	Address	Permission	Description
PASS0_SAR1_CH2_TR_CTL	0x40901880	FULL	Trigger control.
PASS0_SAR1_CH2_SAMPLE_CTL	0x40901884	FULL	Sample control.
PASS0_SAR1_CH2_POST_CTL	0x40901888	FULL	Post processing control
PASS0_SAR1_CH2_RANGE_CTL	0x4090188C	FULL	Range thresholds
PASS0_SAR1_CH2_INTR	0x40901890	FULL	Interrupt request register.
PASS0_SAR1_CH2_INTR_SET	0x40901894	FULL	Interrupt set request register
PASS0_SAR1_CH2_INTR_MASK	0x40901898	FULL	Interrupt mask register.
PASS0_SAR1_CH2_INTR_MASKED	0x4090189C	FULL	Interrupt masked request register
PASS0_SAR1_CH2_WORK	0x409018A0	FULL	Working data register
PASS0_SAR1_CH2_RESULT	0x409018A4	FULL	Result data register
PASS0_SAR1_CH2_GRP_STAT	0x409018A8	FULL	Group status register
PASS0_SAR1_CH2_ENABLE	0x409018B8	FULL	Enable register
PASS0_SAR1_CH2_TR_CMD	0x409018BC	FULL	Software triggers

19.2.4 CH 3

Register Name	Address	Permission	Description
PASS0_SAR1_CH3_TR_CTL	0x409018C0	FULL	Trigger control.
PASS0_SAR1_CH3_SAMPLE_CTL	0x409018C4	FULL	Sample control.
PASS0_SAR1_CH3_POST_CTL	0x409018C8	FULL	Post processing control
PASS0_SAR1_CH3_RANGE_CTL	0x409018CC	FULL	Range thresholds
PASS0_SAR1_CH3_INTR	0x409018D0	FULL	Interrupt request register.
PASS0_SAR1_CH3_INTR_SET	0x409018D4	FULL	Interrupt set request register
PASS0_SAR1_CH3_INTR_MASK	0x409018D8	FULL	Interrupt mask register.
PASS0_SAR1_CH3_INTR_MASKED	0x409018DC	FULL	Interrupt masked request register
PASS0_SAR1_CH3_WORK	0x409018E0	FULL	Working data register
PASS0_SAR1_CH3_RESULT	0x409018E4	FULL	Result data register
PASS0_SAR1_CH3_GRP_STAT	0x409018E8	FULL	Group status register
PASS0_SAR1_CH3_ENABLE	0x409018F8	FULL	Enable register
PASS0_SAR1_CH3_TR_CMD	0x409018FC	FULL	Software triggers

19.2.5 CH 4

Register Name	Address	Permission	Description
PASS0_SAR1_CH4_TR_CTL	0x40901900	FULL	Trigger control.
PASS0_SAR1_CH4_SAMPLE_CTL	0x40901904	FULL	Sample control.
PASS0_SAR1_CH4_POST_CTL	0x40901908	FULL	Post processing control
PASS0_SAR1_CH4_RANGE_CTL	0x4090190C	FULL	Range thresholds
PASS0_SAR1_CH4_INTR	0x40901910	FULL	Interrupt request register.
PASS0_SAR1_CH4_INTR_SET	0x40901914	FULL	Interrupt set request register
PASS0_SAR1_CH4_INTR_MASK	0x40901918	FULL	Interrupt mask register.
PASS0_SAR1_CH4_INTR_MASKED	0x4090191C	FULL	Interrupt masked request register

Register Name	Address	Permission	Description
PASS0_SAR1_CH4_WORK	0x40901920	FULL	Working data register
PASS0_SAR1_CH4_RESULT	0x40901924	FULL	Result data register
PASS0_SAR1_CH4_GRP_STAT	0x40901928	FULL	Group status register
PASS0_SAR1_CH4_ENABLE	0x40901938	FULL	Enable register
PASS0_SAR1_CH4_TR_CMD	0x4090193C	FULL	Software triggers

19.2.6 CH 5

Register Name	Address	Permission	Description
PASS0_SAR1_CH5_TR_CTL	0x40901940	FULL	Trigger control.
PASS0_SAR1_CH5_SAMPLE_CTL	0x40901944	FULL	Sample control.
PASS0_SAR1_CH5_POST_CTL	0x40901948	FULL	Post processing control
PASS0_SAR1_CH5_RANGE_CTL	0x4090194C	FULL	Range thresholds
PASS0_SAR1_CH5_INTR	0x40901950	FULL	Interrupt request register.
PASS0_SAR1_CH5_INTR_SET	0x40901954	FULL	Interrupt set request register
PASS0_SAR1_CH5_INTR_MASK	0x40901958	FULL	Interrupt mask register.
PASS0_SAR1_CH5_INTR_MASKED	0x4090195C	FULL	Interrupt masked request register
PASS0_SAR1_CH5_WORK	0x40901960	FULL	Working data register
PASS0_SAR1_CH5_RESULT	0x40901964	FULL	Result data register
PASS0_SAR1_CH5_GRP_STAT	0x40901968	FULL	Group status register
PASS0_SAR1_CH5_ENABLE	0x40901978	FULL	Enable register
PASS0_SAR1_CH5_TR_CMD	0x4090197C	FULL	Software triggers

19.2.7 CH 6

Register Name	Address	Permission	Description
PASS0_SAR1_CH6_TR_CTL	0x40901980	FULL	Trigger control.
PASS0_SAR1_CH6_SAMPLE_CTL	0x40901984	FULL	Sample control.
PASS0_SAR1_CH6_POST_CTL	0x40901988	FULL	Post processing control
PASS0_SAR1_CH6_RANGE_CTL	0x4090198C	FULL	Range thresholds
PASS0_SAR1_CH6_INTR	0x40901990	FULL	Interrupt request register.
PASS0_SAR1_CH6_INTR_SET	0x40901994	FULL	Interrupt set request register
PASS0_SAR1_CH6_INTR_MASK	0x40901998	FULL	Interrupt mask register.
PASS0_SAR1_CH6_INTR_MASKED	0x4090199C	FULL	Interrupt masked request register
PASS0_SAR1_CH6_WORK	0x409019A0	FULL	Working data register
PASS0_SAR1_CH6_RESULT	0x409019A4	FULL	Result data register
PASS0_SAR1_CH6_GRP_STAT	0x409019A8	FULL	Group status register
PASS0_SAR1_CH6_ENABLE	0x409019B8	FULL	Enable register
PASS0_SAR1_CH6_TR_CMD	0x409019BC	FULL	Software triggers

19.2.8 CH 7

Register Name	Address	Permission	Description
PASS0_SAR1_CH7_TR_CTL	0x409019C0	FULL	Trigger control.
PASS0_SAR1_CH7_SAMPLE_CTL	0x409019C4	FULL	Sample control.
PASS0_SAR1_CH7_POST_CTL	0x409019C8	FULL	Post processing control
PASS0_SAR1_CH7_RANGE_CTL	0x409019CC	FULL	Range thresholds
PASS0_SAR1_CH7_INTR	0x409019D0	FULL	Interrupt request register.
PASS0_SAR1_CH7_INTR_SET	0x409019D4	FULL	Interrupt set request register
PASS0_SAR1_CH7_INTR_MASK	0x409019D8	FULL	Interrupt mask register.
PASS0_SAR1_CH7_INTR_MASKED	0x409019DC	FULL	Interrupt masked request register
PASS0_SAR1_CH7_WORK	0x409019E0	FULL	Working data register
PASS0_SAR1_CH7_RESULT	0x409019E4	FULL	Result data register
PASS0_SAR1_CH7_GRP_STAT	0x409019E8	FULL	Group status register
PASS0_SAR1_CH7_ENABLE	0x409019F8	FULL	Enable register
PASS0_SAR1_CH7_TR_CMD	0x409019FC	FULL	Software triggers

19.2.9 CH 8

Register Name	Address	Permission	Description
PASS0_SAR1_CH8_TR_CTL	0x40901A00	FULL	Trigger control.
PASS0_SAR1_CH8_SAMPLE_CTL	0x40901A04	FULL	Sample control.
PASS0_SAR1_CH8_POST_CTL	0x40901A08	FULL	Post processing control
PASS0_SAR1_CH8_RANGE_CTL	0x40901A0C	FULL	Range thresholds
PASS0_SAR1_CH8_INTR	0x40901A10	FULL	Interrupt request register.
PASS0_SAR1_CH8_INTR_SET	0x40901A14	FULL	Interrupt set request register
PASS0_SAR1_CH8_INTR_MASK	0x40901A18	FULL	Interrupt mask register.

Register Name	Address	Permission	Description
PASS0_SAR1_CH8_INTR_MASKED	0x40901A1C	FULL	Interrupt masked request register
PASS0_SAR1_CH8_WORK	0x40901A20	FULL	Working data register
PASS0_SAR1_CH8_RESULT	0x40901A24	FULL	Result data register
PASS0_SAR1_CH8_GRP_STAT	0x40901A28	FULL	Group status register
PASS0_SAR1_CH8_ENABLE	0x40901A38	FULL	Enable register
PASS0_SAR1_CH8_TR_CMD	0x40901A3C	FULL	Software triggers

19.2.10 CH 9

Register Name	Address	Permission	Description
PASS0_SAR1_CH9_TR_CTL	0x40901A40	FULL	Trigger control.
PASS0_SAR1_CH9_SAMPLE_CTL	0x40901A44	FULL	Sample control.
PASS0_SAR1_CH9_POST_CTL	0x40901A48	FULL	Post processing control
PASS0_SAR1_CH9_RANGE_CTL	0x40901A4C	FULL	Range thresholds
PASS0_SAR1_CH9_INTR	0x40901A50	FULL	Interrupt request register.
PASS0_SAR1_CH9_INTR_SET	0x40901A54	FULL	Interrupt set request register
PASS0_SAR1_CH9_INTR_MASK	0x40901A58	FULL	Interrupt mask register.
PASS0_SAR1_CH9_INTR_MASKED	0x40901A5C	FULL	Interrupt masked request register
PASS0_SAR1_CH9_WORK	0x40901A60	FULL	Working data register
PASS0_SAR1_CH9_RESULT	0x40901A64	FULL	Result data register
PASS0_SAR1_CH9_GRP_STAT	0x40901A68	FULL	Group status register
PASS0_SAR1_CH9_ENABLE	0x40901A78	FULL	Enable register
PASS0_SAR1_CH9_TR_CMD	0x40901A7C	FULL	Software triggers

19.2.11 CH 10

Register Name	Address	Permission	Description
PASS0_SAR1_CH10_TR_CTL	0x40901A80	FULL	Trigger control.
PASS0_SAR1_CH10_SAMPLE_CTL	0x40901A84	FULL	Sample control.
PASS0_SAR1_CH10_POST_CTL	0x40901A88	FULL	Post processing control
PASS0_SAR1_CH10_RANGE_CTL	0x40901A8C	FULL	Range thresholds
PASS0_SAR1_CH10_INTR	0x40901A90	FULL	Interrupt request register.
PASS0_SAR1_CH10_INTR_SET	0x40901A94	FULL	Interrupt set request register
PASS0_SAR1_CH10_INTR_MASK	0x40901A98	FULL	Interrupt mask register.
PASS0_SAR1_CH10_INTR_MASKED	0x40901A9C	FULL	Interrupt masked request register
PASS0_SAR1_CH10_WORK	0x40901AA0	FULL	Working data register
PASS0_SAR1_CH10_RESULT	0x40901AA4	FULL	Result data register
PASS0_SAR1_CH10_GRP_STAT	0x40901AA8	FULL	Group status register
PASS0_SAR1_CH10_ENABLE	0x40901AB8	FULL	Enable register
PASS0_SAR1_CH10_TR_CMD	0x40901ABC	FULL	Software triggers

19.2.12 CH 11

Register Name	Address	Permission	Description
PASS0_SAR1_CH11_TR_CTL	0x40901AC0	FULL	Trigger control.
PASS0_SAR1_CH11_SAMPLE_CTL	0x40901AC4	FULL	Sample control.
PASS0_SAR1_CH11_POST_CTL	0x40901AC8	FULL	Post processing control
PASS0_SAR1_CH11_RANGE_CTL	0x40901ACC	FULL	Range thresholds
PASS0_SAR1_CH11_INTR	0x40901AD0	FULL	Interrupt request register.
PASS0_SAR1_CH11_INTR_SET	0x40901AD4	FULL	Interrupt set request register
PASS0_SAR1_CH11_INTR_MASK	0x40901AD8	FULL	Interrupt mask register.
PASS0_SAR1_CH11_INTR_MASKED	0x40901ADC	FULL	Interrupt masked request register
PASS0_SAR1_CH11_WORK	0x40901AE0	FULL	Working data register
PASS0_SAR1_CH11_RESULT	0x40901AE4	FULL	Result data register
PASS0_SAR1_CH11_GRP_STAT	0x40901AE8	FULL	Group status register
PASS0_SAR1_CH11_ENABLE	0x40901AF8	FULL	Enable register
PASS0_SAR1_CH11_TR_CMD	0x40901AFC	FULL	Software triggers

19.2.13 CH 12

Register Name	Address	Permission	Description
PASS0_SAR1_CH12_TR_CTL	0x40901B00	FULL	Trigger control.
PASS0_SAR1_CH12_SAMPLE_CTL	0x40901B04	FULL	Sample control.
PASS0_SAR1_CH12_POST_CTL	0x40901B08	FULL	Post processing control
PASS0_SAR1_CH12_RANGE_CTL	0x40901B0C	FULL	Range thresholds
PASS0_SAR1_CH12_INTR	0x40901B10	FULL	Interrupt request register.
PASS0_SAR1_CH12_INTR_SET	0x40901B14	FULL	Interrupt set request register

Register Name	Address	Permission	Description
PASS0_SAR1_CH12_INTR_MASK	0x40901B18	FULL	Interrupt mask register.
PASS0_SAR1_CH12_INTR_MASKED	0x40901B1C	FULL	Interrupt masked request register
PASS0_SAR1_CH12_WORK	0x40901B20	FULL	Working data register
PASS0_SAR1_CH12_RESULT	0x40901B24	FULL	Result data register
PASS0_SAR1_CH12_GRP_STAT	0x40901B28	FULL	Group status register
PASS0_SAR1_CH12_ENABLE	0x40901B38	FULL	Enable register
PASS0_SAR1_CH12_TR_CMD	0x40901B3C	FULL	Software triggers

19.2.14 CH 13

Register Name	Address	Permission	Description
PASS0_SAR1_CH13_TR_CTL	0x40901B40	FULL	Trigger control.
PASS0_SAR1_CH13_SAMPLE_CTL	0x40901B44	FULL	Sample control.
PASS0_SAR1_CH13_POST_CTL	0x40901B48	FULL	Post processing control
PASS0_SAR1_CH13_RANGE_CTL	0x40901B4C	FULL	Range thresholds
PASS0_SAR1_CH13_INTR	0x40901B50	FULL	Interrupt request register.
PASS0_SAR1_CH13_INTR_SET	0x40901B54	FULL	Interrupt set request register
PASS0_SAR1_CH13_INTR_MASK	0x40901B58	FULL	Interrupt mask register.
PASS0_SAR1_CH13_INTR_MASKED	0x40901B5C	FULL	Interrupt masked request register
PASS0_SAR1_CH13_WORK	0x40901B60	FULL	Working data register
PASS0_SAR1_CH13_RESULT	0x40901B64	FULL	Result data register
PASS0_SAR1_CH13_GRP_STAT	0x40901B68	FULL	Group status register
PASS0_SAR1_CH13_ENABLE	0x40901B78	FULL	Enable register
PASS0_SAR1_CH13_TR_CMD	0x40901B7C	FULL	Software triggers

19.2.15 CH 14

Register Name	Address	Permission	Description
PASS0_SAR1_CH14_TR_CTL	0x40901B80	FULL	Trigger control.
PASS0_SAR1_CH14_SAMPLE_CTL	0x40901B84	FULL	Sample control.
PASS0_SAR1_CH14_POST_CTL	0x40901B88	FULL	Post processing control
PASS0_SAR1_CH14_RANGE_CTL	0x40901B8C	FULL	Range thresholds
PASS0_SAR1_CH14_INTR	0x40901B90	FULL	Interrupt request register.
PASS0_SAR1_CH14_INTR_SET	0x40901B94	FULL	Interrupt set request register
PASS0_SAR1_CH14_INTR_MASK	0x40901B98	FULL	Interrupt mask register.
PASS0_SAR1_CH14_INTR_MASKED	0x40901B9C	FULL	Interrupt masked request register
PASS0_SAR1_CH14_WORK	0x40901BA0	FULL	Working data register
PASS0_SAR1_CH14_RESULT	0x40901BA4	FULL	Result data register
PASS0_SAR1_CH14_GRP_STAT	0x40901BA8	FULL	Group status register
PASS0_SAR1_CH14_ENABLE	0x40901BB8	FULL	Enable register
PASS0_SAR1_CH14_TR_CMD	0x40901BBC	FULL	Software triggers

19.2.16 CH 15

Register Name	Address	Permission	Description
PASS0_SAR1_CH15_TR_CTL	0x40901BC0	FULL	Trigger control.
PASS0_SAR1_CH15_SAMPLE_CTL	0x40901BC4	FULL	Sample control.
PASS0_SAR1_CH15_POST_CTL	0x40901BC8	FULL	Post processing control
PASS0_SAR1_CH15_RANGE_CTL	0x40901BCC	FULL	Range thresholds
PASS0_SAR1_CH15_INTR	0x40901BD0	FULL	Interrupt request register.
PASS0_SAR1_CH15_INTR_SET	0x40901BD4	FULL	Interrupt set request register
PASS0_SAR1_CH15_INTR_MASK	0x40901BD8	FULL	Interrupt mask register.
PASS0_SAR1_CH15_INTR_MASKED	0x40901BDC	FULL	Interrupt masked request register
PASS0_SAR1_CH15_WORK	0x40901BE0	FULL	Working data register
PASS0_SAR1_CH15_RESULT	0x40901BE4	FULL	Result data register
PASS0_SAR1_CH15_GRP_STAT	0x40901BE8	FULL	Group status register
PASS0_SAR1_CH15_ENABLE	0x40901BF8	FULL	Enable register
PASS0_SAR1_CH15_TR_CMD	0x40901BFC	FULL	Software triggers

19.2.17 CH 16

Register Name	Address	Permission	Description
PASS0_SAR1_CH16_TR_CTL	0x40901C00	FULL	Trigger control.
PASS0_SAR1_CH16_SAMPLE_CTL	0x40901C04	FULL	Sample control.
PASS0_SAR1_CH16_POST_CTL	0x40901C08	FULL	Post processing control
PASS0_SAR1_CH16_RANGE_CTL	0x40901C0C	FULL	Range thresholds
PASS0_SAR1_CH16_INTR	0x40901C10	FULL	Interrupt request register.

Register Name	Address	Permission	Description
PASS0_SAR1_CH16_INTR_SET	0x40901C14	FULL	Interrupt set request register
PASS0_SAR1_CH16_INTR_MASK	0x40901C18	FULL	Interrupt mask register.
PASS0_SAR1_CH16_INTR_MASKED	0x40901C1C	FULL	Interrupt masked request register
PASS0_SAR1_CH16_WORK	0x40901C20	FULL	Working data register
PASS0_SAR1_CH16_RESULT	0x40901C24	FULL	Result data register
PASS0_SAR1_CH16_GRP_STAT	0x40901C28	FULL	Group status register
PASS0_SAR1_CH16_ENABLE	0x40901C38	FULL	Enable register
PASS0_SAR1_CH16_TR_CMD	0x40901C3C	FULL	Software triggers

19.2.18 CH 17

Register Name	Address	Permission	Description
PASS0_SAR1_CH17_TR_CTL	0x40901C40	FULL	Trigger control.
PASS0_SAR1_CH17_SAMPLE_CTL	0x40901C44	FULL	Sample control.
PASS0_SAR1_CH17_POST_CTL	0x40901C48	FULL	Post processing control
PASS0_SAR1_CH17_RANGE_CTL	0x40901C4C	FULL	Range thresholds
PASS0_SAR1_CH17_INTR	0x40901C50	FULL	Interrupt request register.
PASS0_SAR1_CH17_INTR_SET	0x40901C54	FULL	Interrupt set request register
PASS0_SAR1_CH17_INTR_MASK	0x40901C58	FULL	Interrupt mask register.
PASS0_SAR1_CH17_INTR_MASKED	0x40901C5C	FULL	Interrupt masked request register
PASS0_SAR1_CH17_WORK	0x40901C60	FULL	Working data register
PASS0_SAR1_CH17_RESULT	0x40901C64	FULL	Result data register
PASS0_SAR1_CH17_GRP_STAT	0x40901C68	FULL	Group status register
PASS0_SAR1_CH17_ENABLE	0x40901C78	FULL	Enable register
PASS0_SAR1_CH17_TR_CMD	0x40901C7C	FULL	Software triggers

19.2.19 CH 18

Register Name	Address	Permission	Description
PASS0_SAR1_CH18_TR_CTL	0x40901C80	FULL	Trigger control.
PASS0_SAR1_CH18_SAMPLE_CTL	0x40901C84	FULL	Sample control.
PASS0_SAR1_CH18_POST_CTL	0x40901C88	FULL	Post processing control
PASS0_SAR1_CH18_RANGE_CTL	0x40901C8C	FULL	Range thresholds
PASS0_SAR1_CH18_INTR	0x40901C90	FULL	Interrupt request register.
PASS0_SAR1_CH18_INTR_SET	0x40901C94	FULL	Interrupt set request register
PASS0_SAR1_CH18_INTR_MASK	0x40901C98	FULL	Interrupt mask register.
PASS0_SAR1_CH18_INTR_MASKED	0x40901C9C	FULL	Interrupt masked request register
PASS0_SAR1_CH18_WORK	0x40901CA0	FULL	Working data register
PASS0_SAR1_CH18_RESULT	0x40901CA4	FULL	Result data register
PASS0_SAR1_CH18_GRP_STAT	0x40901CA8	FULL	Group status register
PASS0_SAR1_CH18_ENABLE	0x40901CB8	FULL	Enable register
PASS0_SAR1_CH18_TR_CMD	0x40901CBC	FULL	Software triggers

19.2.20 CH 19

Register Name	Address	Permission	Description
PASS0_SAR1_CH19_TR_CTL	0x40901CC0	FULL	Trigger control.
PASS0_SAR1_CH19_SAMPLE_CTL	0x40901CC4	FULL	Sample control.
PASS0_SAR1_CH19_POST_CTL	0x40901CC8	FULL	Post processing control
PASS0_SAR1_CH19_RANGE_CTL	0x40901CCC	FULL	Range thresholds
PASS0_SAR1_CH19_INTR	0x40901CD0	FULL	Interrupt request register.
PASS0_SAR1_CH19_INTR_SET	0x40901CD4	FULL	Interrupt set request register
PASS0_SAR1_CH19_INTR_MASK	0x40901CD8	FULL	Interrupt mask register.
PASS0_SAR1_CH19_INTR_MASKED	0x40901CDC	FULL	Interrupt masked request register
PASS0_SAR1_CH19_WORK	0x40901CE0	FULL	Working data register
PASS0_SAR1_CH19_RESULT	0x40901CE4	FULL	Result data register
PASS0_SAR1_CH19_GRP_STAT	0x40901CE8	FULL	Group status register
PASS0_SAR1_CH19_ENABLE	0x40901CF8	FULL	Enable register
PASS0_SAR1_CH19_TR_CMD	0x40901CFC	FULL	Software triggers

19.2.21 CH 20

Register Name	Address	Permission	Description
PASS0_SAR1_CH20_TR_CTL	0x40901D00	FULL	Trigger control.
PASS0_SAR1_CH20_SAMPLE_CTL	0x40901D04	FULL	Sample control.
PASS0_SAR1_CH20_POST_CTL	0x40901D08	FULL	Post processing control
PASS0_SAR1_CH20_RANGE_CTL	0x40901D0C	FULL	Range thresholds

Register Name	Address	Permission	Description
PASS0_SAR1_CH20_INTR	0x40901D10	FULL	Interrupt request register.
PASS0_SAR1_CH20_INTR_SET	0x40901D14	FULL	Interrupt set request register
PASS0_SAR1_CH20_INTR_MASK	0x40901D18	FULL	Interrupt mask register.
PASS0_SAR1_CH20_INTR_MASKED	0x40901D1C	FULL	Interrupt masked request register
PASS0_SAR1_CH20_WORK	0x40901D20	FULL	Working data register
PASS0_SAR1_CH20_RESULT	0x40901D24	FULL	Result data register
PASS0_SAR1_CH20_GRP_STAT	0x40901D28	FULL	Group status register
PASS0_SAR1_CH20_ENABLE	0x40901D38	FULL	Enable register
PASS0_SAR1_CH20_TR_CMD	0x40901D3C	FULL	Software triggers

19.2.22 CH 21

Register Name	Address	Permission	Description
PASS0_SAR1_CH21_TR_CTL	0x40901D40	FULL	Trigger control.
PASS0_SAR1_CH21_SAMPLE_CTL	0x40901D44	FULL	Sample control.
PASS0_SAR1_CH21_POST_CTL	0x40901D48	FULL	Post processing control
PASS0_SAR1_CH21_RANGE_CTL	0x40901D4C	FULL	Range thresholds
PASS0_SAR1_CH21_INTR	0x40901D50	FULL	Interrupt request register.
PASS0_SAR1_CH21_INTR_SET	0x40901D54	FULL	Interrupt set request register
PASS0_SAR1_CH21_INTR_MASK	0x40901D58	FULL	Interrupt mask register.
PASS0_SAR1_CH21_INTR_MASKED	0x40901D5C	FULL	Interrupt masked request register
PASS0_SAR1_CH21_WORK	0x40901D60	FULL	Working data register
PASS0_SAR1_CH21_RESULT	0x40901D64	FULL	Result data register
PASS0_SAR1_CH21_GRP_STAT	0x40901D68	FULL	Group status register
PASS0_SAR1_CH21_ENABLE	0x40901D78	FULL	Enable register
PASS0_SAR1_CH21_TR_CMD	0x40901D7C	FULL	Software triggers

19.2.23 CH 22

Register Name	Address	Permission	Description
PASS0_SAR1_CH22_TR_CTL	0x40901D80	FULL	Trigger control.
PASS0_SAR1_CH22_SAMPLE_CTL	0x40901D84	FULL	Sample control.
PASS0_SAR1_CH22_POST_CTL	0x40901D88	FULL	Post processing control
PASS0_SAR1_CH22_RANGE_CTL	0x40901D8C	FULL	Range thresholds
PASS0_SAR1_CH22_INTR	0x40901D90	FULL	Interrupt request register.
PASS0_SAR1_CH22_INTR_SET	0x40901D94	FULL	Interrupt set request register
PASS0_SAR1_CH22_INTR_MASK	0x40901D98	FULL	Interrupt mask register.
PASS0_SAR1_CH22_INTR_MASKED	0x40901D9C	FULL	Interrupt masked request register
PASS0_SAR1_CH22_WORK	0x40901DA0	FULL	Working data register
PASS0_SAR1_CH22_RESULT	0x40901DA4	FULL	Result data register
PASS0_SAR1_CH22_GRP_STAT	0x40901DA8	FULL	Group status register
PASS0_SAR1_CH22_ENABLE	0x40901DB8	FULL	Enable register
PASS0_SAR1_CH22_TR_CMD	0x40901DBC	FULL	Software triggers

19.2.24 CH 23

Register Name	Address	Permission	Description
PASS0_SAR1_CH23_TR_CTL	0x40901DC0	FULL	Trigger control.
PASS0_SAR1_CH23_SAMPLE_CTL	0x40901DC4	FULL	Sample control.
PASS0_SAR1_CH23_POST_CTL	0x40901DC8	FULL	Post processing control
PASS0_SAR1_CH23_RANGE_CTL	0x40901DCC	FULL	Range thresholds
PASS0_SAR1_CH23_INTR	0x40901DD0	FULL	Interrupt request register.
PASS0_SAR1_CH23_INTR_SET	0x40901DD4	FULL	Interrupt set request register
PASS0_SAR1_CH23_INTR_MASK	0x40901DD8	FULL	Interrupt mask register.
PASS0_SAR1_CH23_INTR_MASKED	0x40901DDC	FULL	Interrupt masked request register
PASS0_SAR1_CH23_WORK	0x40901DE0	FULL	Working data register
PASS0_SAR1_CH23_RESULT	0x40901DE4	FULL	Result data register
PASS0_SAR1_CH23_GRP_STAT	0x40901DE8	FULL	Group status register
PASS0_SAR1_CH23_ENABLE	0x40901DF8	FULL	Enable register
PASS0_SAR1_CH23_TR_CMD	0x40901DFC	FULL	Software triggers

19.2.25 CH 24

Register Name	Address	Permission	Description
PASS0_SAR1_CH24_TR_CTL	0x40901E00	FULL	Trigger control.
PASS0_SAR1_CH24_SAMPLE_CTL	0x40901E04	FULL	Sample control.
PASS0_SAR1_CH24_POST_CTL	0x40901E08	FULL	Post processing control

Register Name	Address	Permission	Description
PASS0_SAR1_CH24_RANGE_CTL	0x40901E0C	FULL	Range thresholds
PASS0_SAR1_CH24_INTR	0x40901E10	FULL	Interrupt request register.
PASS0_SAR1_CH24_INTR_SET	0x40901E14	FULL	Interrupt set request register
PASS0_SAR1_CH24_INTR_MASK	0x40901E18	FULL	Interrupt mask register.
PASS0_SAR1_CH24_INTR_MASKED	0x40901E1C	FULL	Interrupt masked request register
PASS0_SAR1_CH24_WORK	0x40901E20	FULL	Working data register
PASS0_SAR1_CH24_RESULT	0x40901E24	FULL	Result data register
PASS0_SAR1_CH24_GRP_STAT	0x40901E28	FULL	Group status register
PASS0_SAR1_CH24_ENABLE	0x40901E38	FULL	Enable register
PASS0_SAR1_CH24_TR_CMD	0x40901E3C	FULL	Software triggers

19.2.26 CH 25

Register Name	Address	Permission	Description
PASS0_SAR1_CH25_TR_CTL	0x40901E40	FULL	Trigger control.
PASS0_SAR1_CH25_SAMPLE_CTL	0x40901E44	FULL	Sample control.
PASS0_SAR1_CH25_POST_CTL	0x40901E48	FULL	Post processing control
PASS0_SAR1_CH25_RANGE_CTL	0x40901E4C	FULL	Range thresholds
PASS0_SAR1_CH25_INTR	0x40901E50	FULL	Interrupt request register.
PASS0_SAR1_CH25_INTR_SET	0x40901E54	FULL	Interrupt set request register
PASS0_SAR1_CH25_INTR_MASK	0x40901E58	FULL	Interrupt mask register.
PASS0_SAR1_CH25_INTR_MASKED	0x40901E5C	FULL	Interrupt masked request register
PASS0_SAR1_CH25_WORK	0x40901E60	FULL	Working data register
PASS0_SAR1_CH25_RESULT	0x40901E64	FULL	Result data register
PASS0_SAR1_CH25_GRP_STAT	0x40901E68	FULL	Group status register
PASS0_SAR1_CH25_ENABLE	0x40901E78	FULL	Enable register
PASS0_SAR1_CH25_TR_CMD	0x40901E7C	FULL	Software triggers

19.2.27 CH 26

Register Name	Address	Permission	Description
PASS0_SAR1_CH26_TR_CTL	0x40901E80	FULL	Trigger control.
PASS0_SAR1_CH26_SAMPLE_CTL	0x40901E84	FULL	Sample control.
PASS0_SAR1_CH26_POST_CTL	0x40901E88	FULL	Post processing control
PASS0_SAR1_CH26_RANGE_CTL	0x40901E8C	FULL	Range thresholds
PASS0_SAR1_CH26_INTR	0x40901E90	FULL	Interrupt request register.
PASS0_SAR1_CH26_INTR_SET	0x40901E94	FULL	Interrupt set request register
PASS0_SAR1_CH26_INTR_MASK	0x40901E98	FULL	Interrupt mask register.
PASS0_SAR1_CH26_INTR_MASKED	0x40901E9C	FULL	Interrupt masked request register
PASS0_SAR1_CH26_WORK	0x40901EA0	FULL	Working data register
PASS0_SAR1_CH26_RESULT	0x40901EA4	FULL	Result data register
PASS0_SAR1_CH26_GRP_STAT	0x40901EA8	FULL	Group status register
PASS0_SAR1_CH26_ENABLE	0x40901EB8	FULL	Enable register
PASS0_SAR1_CH26_TR_CMD	0x40901EBC	FULL	Software triggers

19.2.28 CH 27

Register Name	Address	Permission	Description
PASS0_SAR1_CH27_TR_CTL	0x40901EC0	FULL	Trigger control.
PASS0_SAR1_CH27_SAMPLE_CTL	0x40901EC4	FULL	Sample control.
PASS0_SAR1_CH27_POST_CTL	0x40901EC8	FULL	Post processing control
PASS0_SAR1_CH27_RANGE_CTL	0x40901EC0	FULL	Range thresholds
PASS0_SAR1_CH27_INTR	0x40901ED0	FULL	Interrupt request register.
PASS0_SAR1_CH27_INTR_SET	0x40901ED4	FULL	Interrupt set request register
PASS0_SAR1_CH27_INTR_MASK	0x40901ED8	FULL	Interrupt mask register.
PASS0_SAR1_CH27_INTR_MASKED	0x40901EDC	FULL	Interrupt masked request register
PASS0_SAR1_CH27_WORK	0x40901EE0	FULL	Working data register
PASS0_SAR1_CH27_RESULT	0x40901EE4	FULL	Result data register
PASS0_SAR1_CH27_GRP_STAT	0x40901EE8	FULL	Group status register
PASS0_SAR1_CH27_ENABLE	0x40901EF8	FULL	Enable register
PASS0_SAR1_CH27_TR_CMD	0x40901EFC	FULL	Software triggers

19.2.29 CH 28

Register Name	Address	Permission	Description
PASS0_SAR1_CH28_TR_CTL	0x40901F00	FULL	Trigger control.
PASS0_SAR1_CH28_SAMPLE_CTL	0x40901F04	FULL	Sample control.

Register Name	Address	Permission	Description
PASS0_SAR1_CH28_POST_CTL	0x40901F08	FULL	Post processing control
PASS0_SAR1_CH28_RANGE_CTL	0x40901F0C	FULL	Range thresholds
PASS0_SAR1_CH28_INTR	0x40901F10	FULL	Interrupt request register.
PASS0_SAR1_CH28_INTR_SET	0x40901F14	FULL	Interrupt set request register
PASS0_SAR1_CH28_INTR_MASK	0x40901F18	FULL	Interrupt mask register.
PASS0_SAR1_CH28_INTR_MASKED	0x40901F1C	FULL	Interrupt masked request register
PASS0_SAR1_CH28_WORK	0x40901F20	FULL	Working data register
PASS0_SAR1_CH28_RESULT	0x40901F24	FULL	Result data register
PASS0_SAR1_CH28_GRP_STAT	0x40901F28	FULL	Group status register
PASS0_SAR1_CH28_ENABLE	0x40901F38	FULL	Enable register
PASS0_SAR1_CH28_TR_CMD	0x40901F3C	FULL	Software triggers

19.2.30 CH 29

Register Name	Address	Permission	Description
PASS0_SAR1_CH29_TR_CTL	0x40901F40	FULL	Trigger control.
PASS0_SAR1_CH29_SAMPLE_CTL	0x40901F44	FULL	Sample control.
PASS0_SAR1_CH29_POST_CTL	0x40901F48	FULL	Post processing control
PASS0_SAR1_CH29_RANGE_CTL	0x40901F4C	FULL	Range thresholds
PASS0_SAR1_CH29_INTR	0x40901F50	FULL	Interrupt request register.
PASS0_SAR1_CH29_INTR_SET	0x40901F54	FULL	Interrupt set request register
PASS0_SAR1_CH29_INTR_MASK	0x40901F58	FULL	Interrupt mask register.
PASS0_SAR1_CH29_INTR_MASKED	0x40901F5C	FULL	Interrupt masked request register
PASS0_SAR1_CH29_WORK	0x40901F60	FULL	Working data register
PASS0_SAR1_CH29_RESULT	0x40901F64	FULL	Result data register
PASS0_SAR1_CH29_GRP_STAT	0x40901F68	FULL	Group status register
PASS0_SAR1_CH29_ENABLE	0x40901F78	FULL	Enable register
PASS0_SAR1_CH29_TR_CMD	0x40901F7C	FULL	Software triggers

19.2.31 CH 30

Register Name	Address	Permission	Description
PASS0_SAR1_CH30_TR_CTL	0x40901F80	FULL	Trigger control.
PASS0_SAR1_CH30_SAMPLE_CTL	0x40901F84	FULL	Sample control.
PASS0_SAR1_CH30_POST_CTL	0x40901F88	FULL	Post processing control
PASS0_SAR1_CH30_RANGE_CTL	0x40901F8C	FULL	Range thresholds
PASS0_SAR1_CH30_INTR	0x40901F90	FULL	Interrupt request register.
PASS0_SAR1_CH30_INTR_SET	0x40901F94	FULL	Interrupt set request register
PASS0_SAR1_CH30_INTR_MASK	0x40901F98	FULL	Interrupt mask register.
PASS0_SAR1_CH30_INTR_MASKED	0x40901F9C	FULL	Interrupt masked request register
PASS0_SAR1_CH30_WORK	0x40901FA0	FULL	Working data register
PASS0_SAR1_CH30_RESULT	0x40901FA4	FULL	Result data register
PASS0_SAR1_CH30_GRP_STAT	0x40901FA8	FULL	Group status register
PASS0_SAR1_CH30_ENABLE	0x40901FB8	FULL	Enable register
PASS0_SAR1_CH30_TR_CMD	0x40901FBC	FULL	Software triggers

19.2.32 CH 31

Register Name	Address	Permission	Description
PASS0_SAR1_CH31_TR_CTL	0x40901FC0	FULL	Trigger control.
PASS0_SAR1_CH31_SAMPLE_CTL	0x40901FC4	FULL	Sample control.
PASS0_SAR1_CH31_POST_CTL	0x40901FC8	FULL	Post processing control
PASS0_SAR1_CH31_RANGE_CTL	0x40901FCC	FULL	Range thresholds
PASS0_SAR1_CH31_INTR	0x40901FD0	FULL	Interrupt request register.
PASS0_SAR1_CH31_INTR_SET	0x40901FD4	FULL	Interrupt set request register
PASS0_SAR1_CH31_INTR_MASK	0x40901FD8	FULL	Interrupt mask register.
PASS0_SAR1_CH31_INTR_MASKED	0x40901FDC	FULL	Interrupt masked request register
PASS0_SAR1_CH31_WORK	0x40901FE0	FULL	Working data register
PASS0_SAR1_CH31_RESULT	0x40901FE4	FULL	Result data register
PASS0_SAR1_CH31_GRP_STAT	0x40901FE8	FULL	Group status register
PASS0_SAR1_CH31_ENABLE	0x40901FF8	FULL	Enable register
PASS0_SAR1_CH31_TR_CMD	0x40901FFC	FULL	Software triggers

19.3 SAR 2

Register Name	Address	Permission	Description
PASS0_SAR2_CTL	0x40902000	FULL	Analog control register.
PASS0_SAR2_DIAG_CTL	0x40902004	FULL	Diagnostic Reference control register.
PASS0_SAR2_PRECOND_CTL	0x40902010	FULL	Preconditioning control register.
PASS0_SAR2_ANA_CAL	0x40902080	FULL	Current analog calibration values
PASS0_SAR2_DIG_CAL	0x40902084	FULL	Current digital calibration values
PASS0_SAR2_ANA_CAL_ALT	0x40902090	FULL	Alternate analog calibration values
PASS0_SAR2_DIG_CAL_ALT	0x40902094	FULL	Alternate digital calibration values
PASS0_SAR2_CAL_UPD_CMD	0x40902098	FULL	Calibration update command
PASS0_SAR2_TR_PEND	0x40902100	FULL	Trigger pending status
PASS0_SAR2_WORK_VALID	0x40902180	FULL	Channel working data register 'valid' bits
PASS0_SAR2_WORK_RANGE	0x40902184	FULL	Range detected
PASS0_SAR2_WORK_RANGE_HI	0x40902188	FULL	Range detect above Hi flag
PASS0_SAR2_WORK_PULSE	0x4090218C	FULL	Pulse detected
PASS0_SAR2_RESULT_VALID	0x409021A0	FULL	Channel result data register 'valid' bits
PASS0_SAR2_RESULT_RANGE_HI	0x409021A4	FULL	Channel Range above Hi flags
PASS0_SAR2_STATUS	0x40902200	FULL	Current status of internal SAR registers (mostly for debug)
PASS0_SAR2_AVG_STAT	0x40902204	FULL	Current averaging status (for debug)

19.3.1 CH 0

Register Name	Address	Permission	Description
PASS0_SAR2_CH0_TR_CTL	0x40902800	FULL	Trigger control.
PASS0_SAR2_CH0_SAMPLE_CTL	0x40902804	FULL	Sample control.
PASS0_SAR2_CH0_POST_CTL	0x40902808	FULL	Post processing control
PASS0_SAR2_CH0_RANGE_CTL	0x4090280C	FULL	Range thresholds
PASS0_SAR2_CH0_INTR	0x40902810	FULL	Interrupt request register.
PASS0_SAR2_CH0_INTR_SET	0x40902814	FULL	Interrupt set request register
PASS0_SAR2_CH0_INTR_MASK	0x40902818	FULL	Interrupt mask register.
PASS0_SAR2_CH0_INTR_MASKED	0x4090281C	FULL	Interrupt masked request register
PASS0_SAR2_CH0_WORK	0x40902820	FULL	Working data register
PASS0_SAR2_CH0_RESULT	0x40902824	FULL	Result data register
PASS0_SAR2_CH0_GRP_STAT	0x40902828	FULL	Group status register
PASS0_SAR2_CH0_ENABLE	0x40902838	FULL	Enable register
PASS0_SAR2_CH0_TR_CMD	0x4090283C	FULL	Software triggers

19.3.2 CH 1

Register Name	Address	Permission	Description
PASS0_SAR2_CH1_TR_CTL	0x40902840	FULL	Trigger control.
PASS0_SAR2_CH1_SAMPLE_CTL	0x40902844	FULL	Sample control.
PASS0_SAR2_CH1_POST_CTL	0x40902848	FULL	Post processing control
PASS0_SAR2_CH1_RANGE_CTL	0x4090284C	FULL	Range thresholds
PASS0_SAR2_CH1_INTR	0x40902850	FULL	Interrupt request register.
PASS0_SAR2_CH1_INTR_SET	0x40902854	FULL	Interrupt set request register
PASS0_SAR2_CH1_INTR_MASK	0x40902858	FULL	Interrupt mask register.
PASS0_SAR2_CH1_INTR_MASKED	0x4090285C	FULL	Interrupt masked request register
PASS0_SAR2_CH1_WORK	0x40902860	FULL	Working data register
PASS0_SAR2_CH1_RESULT	0x40902864	FULL	Result data register
PASS0_SAR2_CH1_GRP_STAT	0x40902868	FULL	Group status register
PASS0_SAR2_CH1_ENABLE	0x40902878	FULL	Enable register
PASS0_SAR2_CH1_TR_CMD	0x4090287C	FULL	Software triggers

19.3.3 CH 2

Register Name	Address	Permission	Description
PASS0_SAR2_CH2_TR_CTL	0x40902880	FULL	Trigger control.
PASS0_SAR2_CH2_SAMPLE_CTL	0x40902884	FULL	Sample control.
PASS0_SAR2_CH2_POST_CTL	0x40902888	FULL	Post processing control
PASS0_SAR2_CH2_RANGE_CTL	0x4090288C	FULL	Range thresholds
PASS0_SAR2_CH2_INTR	0x40902890	FULL	Interrupt request register.
PASS0_SAR2_CH2_INTR_SET	0x40902894	FULL	Interrupt set request register
PASS0_SAR2_CH2_INTR_MASK	0x40902898	FULL	Interrupt mask register.
PASS0_SAR2_CH2_INTR_MASKED	0x4090289C	FULL	Interrupt masked request register
PASS0_SAR2_CH2_WORK	0x409028A0	FULL	Working data register
PASS0_SAR2_CH2_RESULT	0x409028A4	FULL	Result data register

Register Name	Address	Permission	Description
PASS0_SAR2_CH2_GRP_STAT	0x409028A8	FULL	Group status register
PASS0_SAR2_CH2_ENABLE	0x409028B8	FULL	Enable register
PASS0_SAR2_CH2_TR_CMD	0x409028BC	FULL	Software triggers

19.3.4 CH 3

Register Name	Address	Permission	Description
PASS0_SAR2_CH3_TR_CTL	0x409028C0	FULL	Trigger control.
PASS0_SAR2_CH3_SAMPLE_CTL	0x409028C4	FULL	Sample control.
PASS0_SAR2_CH3_POST_CTL	0x409028C8	FULL	Post processing control
PASS0_SAR2_CH3_RANGE_CTL	0x409028CC	FULL	Range thresholds
PASS0_SAR2_CH3_INTR	0x409028D0	FULL	Interrupt request register.
PASS0_SAR2_CH3_INTR_SET	0x409028D4	FULL	Interrupt set request register
PASS0_SAR2_CH3_INTR_MASK	0x409028D8	FULL	Interrupt mask register.
PASS0_SAR2_CH3_INTR_MASKED	0x409028DC	FULL	Interrupt masked request register
PASS0_SAR2_CH3_WORK	0x409028E0	FULL	Working data register
PASS0_SAR2_CH3_RESULT	0x409028E4	FULL	Result data register
PASS0_SAR2_CH3_GRP_STAT	0x409028E8	FULL	Group status register
PASS0_SAR2_CH3_ENABLE	0x409028F8	FULL	Enable register
PASS0_SAR2_CH3_TR_CMD	0x409028FC	FULL	Software triggers

19.3.5 CH 4

Register Name	Address	Permission	Description
PASS0_SAR2_CH4_TR_CTL	0x40902900	FULL	Trigger control.
PASS0_SAR2_CH4_SAMPLE_CTL	0x40902904	FULL	Sample control.
PASS0_SAR2_CH4_POST_CTL	0x40902908	FULL	Post processing control
PASS0_SAR2_CH4_RANGE_CTL	0x4090290C	FULL	Range thresholds
PASS0_SAR2_CH4_INTR	0x40902910	FULL	Interrupt request register.
PASS0_SAR2_CH4_INTR_SET	0x40902914	FULL	Interrupt set request register
PASS0_SAR2_CH4_INTR_MASK	0x40902918	FULL	Interrupt mask register.
PASS0_SAR2_CH4_INTR_MASKED	0x4090291C	FULL	Interrupt masked request register
PASS0_SAR2_CH4_WORK	0x40902920	FULL	Working data register
PASS0_SAR2_CH4_RESULT	0x40902924	FULL	Result data register
PASS0_SAR2_CH4_GRP_STAT	0x40902928	FULL	Group status register
PASS0_SAR2_CH4_ENABLE	0x40902938	FULL	Enable register
PASS0_SAR2_CH4_TR_CMD	0x4090293C	FULL	Software triggers

19.3.6 CH 5

Register Name	Address	Permission	Description
PASS0_SAR2_CH5_TR_CTL	0x40902940	FULL	Trigger control.
PASS0_SAR2_CH5_SAMPLE_CTL	0x40902944	FULL	Sample control.
PASS0_SAR2_CH5_POST_CTL	0x40902948	FULL	Post processing control
PASS0_SAR2_CH5_RANGE_CTL	0x4090294C	FULL	Range thresholds
PASS0_SAR2_CH5_INTR	0x40902950	FULL	Interrupt request register.
PASS0_SAR2_CH5_INTR_SET	0x40902954	FULL	Interrupt set request register
PASS0_SAR2_CH5_INTR_MASK	0x40902958	FULL	Interrupt mask register.
PASS0_SAR2_CH5_INTR_MASKED	0x4090295C	FULL	Interrupt masked request register
PASS0_SAR2_CH5_WORK	0x40902960	FULL	Working data register
PASS0_SAR2_CH5_RESULT	0x40902964	FULL	Result data register
PASS0_SAR2_CH5_GRP_STAT	0x40902968	FULL	Group status register
PASS0_SAR2_CH5_ENABLE	0x40902978	FULL	Enable register
PASS0_SAR2_CH5_TR_CMD	0x4090297C	FULL	Software triggers

19.3.7 CH 6

Register Name	Address	Permission	Description
PASS0_SAR2_CH6_TR_CTL	0x40902980	FULL	Trigger control.
PASS0_SAR2_CH6_SAMPLE_CTL	0x40902984	FULL	Sample control.
PASS0_SAR2_CH6_POST_CTL	0x40902988	FULL	Post processing control
PASS0_SAR2_CH6_RANGE_CTL	0x4090298C	FULL	Range thresholds
PASS0_SAR2_CH6_INTR	0x40902990	FULL	Interrupt request register.
PASS0_SAR2_CH6_INTR_SET	0x40902994	FULL	Interrupt set request register
PASS0_SAR2_CH6_INTR_MASK	0x40902998	FULL	Interrupt mask register.
PASS0_SAR2_CH6_INTR_MASKED	0x4090299C	FULL	Interrupt masked request register
PASS0_SAR2_CH6_WORK	0x409029A0	FULL	Working data register

Register Name	Address	Permission	Description
PASS0_SAR2_CH6_RESULT	0x409029A4	FULL	Result data register
PASS0_SAR2_CH6_GRP_STAT	0x409029A8	FULL	Group status register
PASS0_SAR2_CH6_ENABLE	0x409029B8	FULL	Enable register
PASS0_SAR2_CH6_TR_CMD	0x409029BC	FULL	Software triggers

19.3.8 CH 7

Register Name	Address	Permission	Description
PASS0_SAR2_CH7_TR_CTL	0x409029C0	FULL	Trigger control.
PASS0_SAR2_CH7_SAMPLE_CTL	0x409029C4	FULL	Sample control.
PASS0_SAR2_CH7_POST_CTL	0x409029C8	FULL	Post processing control
PASS0_SAR2_CH7_RANGE_CTL	0x409029CC	FULL	Range thresholds
PASS0_SAR2_CH7_INTR	0x409029D0	FULL	Interrupt request register.
PASS0_SAR2_CH7_INTR_SET	0x409029D4	FULL	Interrupt set request register
PASS0_SAR2_CH7_INTR_MASK	0x409029D8	FULL	Interrupt mask register.
PASS0_SAR2_CH7_INTR_MASKED	0x409029DC	FULL	Interrupt masked request register
PASS0_SAR2_CH7_WORK	0x409029E0	FULL	Working data register
PASS0_SAR2_CH7_RESULT	0x409029E4	FULL	Result data register
PASS0_SAR2_CH7_GRP_STAT	0x409029E8	FULL	Group status register
PASS0_SAR2_CH7_ENABLE	0x409029F8	FULL	Enable register
PASS0_SAR2_CH7_TR_CMD	0x409029FC	FULL	Software triggers

19.4 EPASS_MMIO

Register Name	Address	Permission	Description
PASS0_PASS_CTL	0x409F0000	FULL	PASS control register
PASS0_SAR_TR_IN_SEL0	0x409F0020	FULL	per SAR generic input trigger select
PASS0_SAR_TR_IN_SEL1	0x409F0024	FULL	per SAR generic input trigger select
PASS0_SAR_TR_IN_SEL2	0x409F0028	FULL	per SAR generic input trigger select
PASS0_SAR_TR_OUT_SEL0	0x409F0040	FULL	per SAR generic output trigger select
PASS0_SAR_TR_OUT_SEL1	0x409F0044	FULL	per SAR generic output trigger select
PASS0_SAR_TR_OUT_SEL2	0x409F0048	FULL	per SAR generic output trigger select

19.5 Register Details

19.5.1 SAR

19.5.1.1 PASS_SAR_CTL

Description: Analog control register.
Address: 0x40900000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PWRUP_TIME [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					HALF_LSB [10:10]	MSB_STRETCH [9:9]	IDLE_PWRDWN [8:8]
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	ADC_EN [30:30]	SARMUX_EN [29:29]	None [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	PWRUP_TIME	RW	RW	0	Number cycles to wait to power up after IDLE_PWRDWN. Check the STATUS.PWRUP_BUSY flag to see if the delay is still in progress. The power up delay is 1 us.
8	IDLE_PWRDWN	RW	RW	0	When idle automatically power down the analog. After an automatic power down a new trigger will power up the analog, however it will take PWRUP_TIME cycles before the first acquisition can be started. Note that re-arbitration happens at that time, i.e. the trigger that caused the power up may not get handled first.
9	MSB_STRETCH	RW	RW	0	When set use 2 cycles for the Most Significant Bit (MSB) - 0: Use 1 clock cycle for MSB - 1: Use 2 clock cycles for MSB
10	HALF_LSB	RW	RW	0	When set take an extra cycle to convert the half LSB and add it to 12-bit result for Missing Code Recovery. This bit should always be set to '1' - 0: disable half LSB conversion (not recommended) - 1: enable half LSB conversion
29	SARMUX_EN	RW	RW	0	Enable the SARMUX (only valid if ENABLED=1) - 0: SARMUX disabled (put analog in power down) - 1: SARMUX enabled.

Bits	Name	SW	HW	Default or Enum	Description
30	ADC_EN	RW	RW	0	Enable the SAR ADC and SAR sequencer (only valid if ENABLED=1) - 0: SARADC and SARSEQ are disabled (put SARADC analog in power down and stop clocks), also clears all pending triggers. - 1: SAR ADC and SARSEQ are enabled. To enable ADC0 to borrow SARMUX1-3 the corresponding ADC_EN must be set to 0.
31	ENABLED	RW	RW	0	- 0: SAR IP disabled (put analog in power down and stop clocks), also clears all pending triggers. - 1: SAR IP enabled.

19.5.1.2 PASS_SAR_DIAG_CTL

Description: Diagnostic Reference control register.
Address: 0x40900004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				DIAG_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DIAG_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	DIAG_SEL	RW	RW	0	Select Diagnostic Reference function
	VREFL			0	DiagOut = VrefL
	VREFH_1DIV8			1	DiagOut = VrefH * 1/8
	VREFH_2DIV8			2	DiagOut = VrefH * 2/8
	VREFH_3DIV8			3	DiagOut = VrefH * 3/8
	VREFH_4DIV8			4	DiagOut = VrefH * 4/8
	VREFH_5DIV8			5	DiagOut = VrefH * 5/8
	VREFH_6DIV8			6	DiagOut = VrefH * 6/8
	VREFH_7DIV8			7	DiagOut = VrefH * 7/8
	VREFH			8	DiagOut = VrefH
	VREFX			9	DiagOut = VrefX = VrefH * 199/200
	VBG			10	DiagOut = Vbg from SRSS
	VIN1			11	DiagOut = Vin1
	VIN2			12	DiagOut = Vin2
	VIN3			13	DiagOut = Vin3
	I_SOURCE			14	DiagOut = Isource (10uA)
	I_SINK			15	DiagOut = Isink (10uA)
31	DIAG_EN	RW	RW	0	Diagnostic Reference enable (only valid if ENABLED=1) - 0: Diagnostic Reference disabled (powered down resistor ladder and current mirrors, DiagOut = Vssa). - 1: Diagnostic Reference enabled, output signal select according to DIAG_SEL (note also EPASS_MMIO.PASS_CTL.REFBUF_EN must be set).

19.5.1.3 PASS_SAR_PRECOND_CTL

Description: Preconditioning control register.
Address: 0x40900010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Precondition time value used when a channel enables preconditioning (PRECOND_MODE)
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				PRECOND_TIME [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PRECOND_TIME	RW	RW	0	Number ADC clock cycles that Preconditioning is done before the sample window starts. If OVERLAP_EN=0 there will be 1 additional break before make cycle between preconditioning and sampling. Note that the minimum value is 1 (0 gives the same result as 1).

19.5.1.4 PASS_SAR_ANA_CAL

Description: Current analog calibration values
Address: 0x40900080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment: Hardware can update this register if software sets the CAL_UPD_CMD.UPDATE
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	AOFFSET [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			AGAIN [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	AOFFSET	RW	RW	0	Analog offset correction
16:20	AGAIN	RW	RW	0	Analog gain correction

19.5.1.5 PASS_SAR_DIG_CAL

Description: Current digital calibration values
Address: 0x40900084
Offset: 0x84
Retention: Retained
IsDeepSleep: No
Comment: Hardware can update this register if software sets the CAL_UPD_CMD.UPDATE
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DOFFSET [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				DOFFSET [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		DGAIN [21:16]					

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:11	DOFFSET	RW	RW	0	Digital offset correction Subtract DOFFSET from ADC output.
16:21	DGAIN	RW	RW	0	Digital gain correction. Signed value to correct +/- 30 codes for the maximum input voltage. Corrected = (D - DOFFSET) + ((D - DOFFSET) * DGAIN + 0x800) / 0x1000

19.5.1.6 PASS_SAR_ANA_CAL_ALT

Description: Alternate analog calibration values
Address: 0x40900090
Offset: 0x90
Retention: Retained
IsDeepSleep: No
Comment: Also known as 'shadow' calibration registers to enable background calibration
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	AOFFSET [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			AGAIN [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	AOFFSET	RW	RW	0	See corresponding ANA_CAL field
16:20	AGAIN	RW	RW	0	See corresponding ANA_CAL field

19.5.1.8 PASS_SAR_CAL_UPD_CMD

Description: Calibration update command
Address: 0x40900098
Offset: 0x98
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							UPDATE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	UPDATE	RW	RW	0	Calibration update command: coherently copy values from alternate calibration regs to current calibration regs. Software sets this bit when the alternate calibration values have been set with the new values. Hardware will do the calibration update as soon as the ADC is idle or a 'continuous' triggered group completes. This ensures that all acquisitions within a group scan (even if preempted) are done with the same calibration values. This bit is cleared at the same time the calibration update is done. By clearing this bit software can cancel a requested update. Note: if the ADC is always busy with acquisitions for non continuously triggered groups/channels then the calibration update will remain pending forever. In such a case the software can either do a non coherent update by writing directly to the current calibration registers, or software can force the ADC to idle by disabling some or all channels. Software can check/poll this bit to see if the calibration update has taken effect.

19.5.1.9 PASS_SAR_TR_PEND

Description: Trigger pending status
Address: 0x40900100
Offset: 0x100
Retention: Not Retained
IsDeepSleep: No
Comment: Status
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TR_PEND [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TR_PEND [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	TR_PEND [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	TR_PEND [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	TR_PEND	R	R	0	Trigger Pending. Hardware will set this bit if a hardware trigger is received.

19.5.1.10 PASS_SAR_WORK_VALID

Description: Channel working data register 'valid' bits
Address: 0x40900180
Offset: 0x180
Retention: Not Retained
IsDeepSleep: No
Comment: bits of disabled channels will be reset
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORK_VALID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	WORK_VALID [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	WORK_VALID [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WORK_VALID [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	WORK_VALID	R	R	0	If set the corresponding WORK register is valid, i.e. was already acquired during the current group scan. If this bit is low then either the channel is not enabled, not yet acquired or it is used as a pulse detect channel.

19.5.1.11 PASS_SAR_WORK_RANGE

Description: Range detected
Address: 0x40900184
Offset: 0x184
Retention: Not Retained
IsDeepSleep: No
Comment: bits of disabled channels will be reset
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RANGE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RANGE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RANGE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RANGE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RANGE	R	R	0	N/A

19.5.1.12 PASS_SAR_WORK_RANGE_HI

Description: Range detect above Hi flag
Address: 0x40900188
Offset: 0x188
Retention: Not Retained
IsDeepSleep: No
Comment: bits of disabled channels will be reset
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ABOVE_HI [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ABOVE_HI [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ABOVE_HI [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ABOVE_HI [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ABOVE_HI	R	R	0	Out of range was detected and the value was above the Hi threshold

19.5.1.13 PASS_SAR_WORK_PULSE

Description: Pulse detected
Address: 0x4090018C
Offset: 0x18C
Retention: Not Retained
IsDeepSleep: No
Comment: bits of disabled channels will be reset
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PULSE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PULSE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PULSE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PULSE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	PULSE	R	R	0	N/A

19.5.1.14 PASS_SAR_RESULT_VALID

Description: Channel result data register 'valid' bits
Address: 0x409001A0
Offset: 0x1A0
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESULT_VALID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESULT_VALID [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESULT_VALID [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESULT_VALID [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESULT_VALID	R	R	0	If set the corresponding RESULT register is valid, i.e. was acquired during the preceding group scan. If this bit is low, after a group scan completed, then either the channel is not enabled or is used as a pulse detect channel.

19.5.1.15 PASS_SAR_RESULT_RANGE_HI

Description: Channel Range above Hi flags
Address: 0x409001A4
Offset: 0x1A4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ABOVE_HI [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ABOVE_HI [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ABOVE_HI [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ABOVE_HI [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ABOVE_HI	R	R	0	Out of range was detected and the value was above the Hi threshold

19.5.1.16 PASS_SAR_STATUS

Description: Current status of internal SAR registers (mostly for debug)
Address: 0x40900200
Offset: 0x200
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			CUR_CHAN [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		CUR_PREEMPT_TYPE [13:12]		None [11:11]	CUR_PRIO [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	PWRUP_BUSY [30:30]	DBG_FREEZE [29:29]	None [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	CUR_CHAN	R	R	0	current channel being acquired, only valid if BUSY.
8:10	CUR_PRIO	R	R	0	priority of current group/channel, only valid if BUSY.
12:13	CUR_PREEMPT_TYPE	R	R	0	Preempting type of current group/channel, only valid if BUSY.
29	DBG_FREEZE	R	R	0	If high then the SAR is prevented from starting a new acquisition, see DBG_FREEZE_EN.
30	PWRUP_BUSY	R	R	0	If high then the SAR is waiting for PWRUP_TIME due to IDLE_PWRDWN
31	BUSY	R	R	0	If high then the SAR is busy with a conversion.

19.5.1.17 PASS_SAR_AVG_STAT

Description: Current averaging status (for debug)
Address: 0x40900204
Offset: 0x204
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUR_AVG_ACCU [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CUR_AVG_ACCU [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				CUR_AVG_ACCU [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	CUR_AVG_CNT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:19	CUR_AVG_ACCU	R	R	0	the current value of the averaging accumulator
24:31	CUR_AVG_CNT	R	R	0	the current value of the averaging counter. Note that the value shown is updated after the sample window and therefore runs ahead of the accumulator update.

19.5.1.18 CH

19.5.1.18.1 PASS_SAR_CH_TR_CTL

Description: Trigger control.
Address: 0x40900800
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Make sure the channel or the IP is disabled before changing this register
Default: 0x800

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	PRIO [6:4]			None [3:3]	SEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				GROUP_END [11:11]	None [10:10]	PREEMPT_TYPE [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DONE_LEVEL [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	SEL	RW	RW	0	Trigger select
	OFF			0	Use for channels in group, except the first channel
	TCPWM			1	Trigger from corresponding TCPWM channel
	GENERIC0			2	Generic trigger input 0
	GENERIC1			3	N/A
	GENERIC2			4	N/A
	GENERIC3			5	N/A
	GENERIC4			6	N/A
	CONTINUOUS			7	Always triggered (also called idle), can only be used for at most 1 channel
4:6	PRIO	RW	RW	0	Channel priority: '0': highest priority. '1' ... '6' '7': lowest priority. Channels with the same priority constitute a priority level. Priority decoding determines the highest priority pending channel. This channel is determined as follows. First, the highest priority level with pending channels is identified. Second, within this priority level, round robin arbitration is applied. Round robin arbitration (within a priority level) gives the highest priority to the lower channel indices (within the priority level).
8:9	PREEMPT_TYPE	RW	RW	0	Preemption type allow for this group

Bits	Name	SW	HW	Default or Enum	Description
	ABORT_CANCEL			0	Abort ongoing acquisition, do not return Clear pending trigger for aborted group and set Cancelled interrupt. Also 'Abort' whenever this group (do not pend the trigger) is not immediately scheduled for acquisition after a new trigger arrives. For this preemption type only, only a positive edge on the trigger can trigger the channel, i.e. CONTINUOUS or level high operation is not supported (to avoid continuous Cancelled interrupts). In case CTL.IDLE_PWRDWN is used and the analog is powered down, the group cannot be immediately scheduled for acquisition and therefore a trigger for a group with this preemption type will power up the analog, but the group will ABORT and set the Cancelled interrupt
	ABORT_RESTART			1	Abort ongoing acquisition, up on return Restart group from first channel.
	ABORT_RESUME			2	Abort ongoing acquisition, up on return Resume group from aborted channel If averaging, discard averaging results so far and restart averaging.
	FINISH_RESUME			3	Complete ongoing acquisition (including averaging), up on return Resume group from next channel
11	GROUP_END	RW	RW	1	0: continue group with next channel 1: last channel of a group. Note that for the channel with the highest index (SAR_CH_NR) this always needs to be set
31	DONE_LEVEL	RW	RW	0	select level or pulse for 'tr_ch_done' trigger output Also see POST_CTL.TR_DONE_GRP_VIO
	PULSE			0	tr_ch_done generates a 2 cycle pulse (clk_sys), no need to read the result to clear (also no ch_overflow detection)
	LEVEL			1	tr_ch_done is a level output until the result register is read (typical for DW usage, this also enables ch_overflow detection when DW is too slow)

19.5.1.18.2 PASS_SAR_CH_SAMPLE_CTL

Description: Sample control.
Address: 0x40900804
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: Make sure the channel or the IP is disabled before changing this register
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PORT_ADDR [7:6]		PIN_ADDR [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	OVERLAP_DIAG [15:14]		PRECOND_MODE [13:12]		EXT_MUX_EN [11:11]	EXT_MUX_SEL [10:8]		

Bits	23	22	21	20	19	18	17	16
Name	SAMPLE_TIME [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ALT_CAL [31:31]	None [30:28]			SAMPLE_TIME [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	PIN_ADDR	RW	RW	Undefined	Address of the analog signal (pin) to be sampled by this channel - 0..31 : Vout = AN0..31, select corresponding analog input - 32: Vout = Vmotor, select motor input - 33: Vout = Vaux, select auxiliary input - 34: Vout = AmuxbusA - 35: Vout = AmuxbusB - 36: Vout = Vccd - 37: Vout = Vdda - 38: Vout = Vbg, Bandgap voltage from SRSS - 39: Vout = Vtemp, select temperature sensor. Make sure that only 1 ADC is allowed to use this. - 40..61: Vout = undefined, reserved for future products - 62: Vout = VrefL (VrefL actually bypasses the SARMUX (XSL)) - 63: Vout = VrefH (VrefH actually bypasses the SARMUX (XSH)) Note: When PORT_ADDR is not set to SARMUX0, pin addresses from 32-63 are not available. Only addresses 0-31 can be accessed from SARMUX1-3
6:7	PORT_ADDR	RW	RW	Undefined	Select the physical port. This field is only valid for ADC0. ADC0 can control and connect to the SARMUX of the neighboring ADC1-3. This requires the corresponding ADC to be off while the SARMUX is left on. When ADC0 controls another SARMUX it uses the PIN_ADDR, EXT_MUX_EN/SEL of this channel to control the other SARMUX.
	SARMUX0			0	ADC uses it's own SARMUX
	SARMUX1			1	ADC0 uses SARMUX1 (only valid for ADC0, undefined result if used for ADC1-3)

Bits	Name	SW	HW	Default or Enum	Description
	SARMUX2			2	ADC0 uses SARMUX2 (only valid for ADC0, undefined result if used for ADC1-3)
	SARMUX3			3	ADC0 uses SARMUX3 (only valid for ADC0, undefined result if used for ADC1-3)
8:10	EXT_MUX_SEL	RW	RW	Undefined	External analog mux select. This bit setting is related to EXT_MUX[x]_y on pin assignment. 0x0: Select EXT_MUX[x]_0 pin 0x1: Select EXT_MUX[x]_1 pin
11	EXT_MUX_EN	RW	RW	Undefined	External analog mux enable. This enable can be used as enable (chip select) for the external analog mux (this enable is not used as enable for the GPIO output driver). This enable also prevents unnecessary toggle activity on the select signals of the external analog mux. When this enable is low EXT_MUX_SEL value will be ignored and the previous value will be maintained. Note that an external analog mux can only be used in combination with a pin input, i.e. PIN_ADDR<32 or Vmotor. If an internal signal is selected this enable should be 0.
12:13	PRECOND_MODE	RW	RW	Undefined	Select preconditioning mode. Preconditioning (dis)charges the SAR sample capacitor to the selected reference voltage for PRECOND_TIME (global) cycles, a break before make cycle will be inserted before sampling starts (SAMPLE_TIME).
	OFF			0	No preconditioning
	VREFL			1	Discharge to VREFL
	VREFH			2	Charge to VREFH
	DIAG			3	Connect the Diagnostic reference output during preconditioning. The Diagnostic reference should be configured to output a reference voltage. Note: this selection is mutual exclusive with using the Diagnostic reference to supply an ibias current for OVERLAP.
14:15	OVERLAP_DIAG	RW	RW	Undefined	Select Overlap mode or SARMUX Diagnostics, in both cases the Diagnostic reference is used. With Overlap the Diagnostic reference typically sources or sinks a small current which is connected at the same time as the analog signal being sampled. For SARMUX Diagnostics the Diagnostic reference should provide a reference voltage which is selected at the SARMUX input instead of the normal analog signal being sampled.
	OFF			0	No overlap or SARMUX Diagnostics
	HALF			1	Sample the selected analog input for 2 SAMPLE_TIME periods. During the first period use overlap sampling, i.e. connect both the analog input and Diagnostic reference. During second period only connect the analog input.
	FULL			2	Like normal sample the selected analog input for a single SAMPLE_TIME period but use overlap sampling, i.e. connect both the analog input and Diagnostic reference.
	MUX_DIAG			3	Select Diagnostic reference instead of analog signal at the input of the SARMUX. This enables a functional safety check of the SARMUX analog connections.

Bits	Name	SW	HW	Default or Enum	Description
16:27	SAMPLE_TIME	RW	RW	Undefined	Sample time (aperture) in ADC clock cycles. Minimum is 1 (0 gives the same result as 1), minimum time needed for proper settling is at least 300ns, i.e. 6 clock cycles at the max frequency of 20MHz.
31	ALT_CAL	RW	RW	Undefined	Use alternate calibration values instead of the current calibration values. This allows the firmware to allocate one or more channels to quietly re-calibrate the ADC in the background of regular processing. 0 = use regular calibration values (ANA/DIG_CAL) 1 = use alternate calibration values (ANA/DIG_CAL_ALT) Note: typically calibration measurements select VrefL (PIN_ADDR=62) or VrefH (PIN_ADDR=63)

19.5.1.18.3 PASS_SAR_CH_POST_CTL

Description: Post processing control
Address: 0x40900808
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: Make sure the channel or the IP is disabled before changing this register
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SIGN_EXT [7:7]	LEFT_ALIGN [6:6]	None [5:3]			POST_PROC [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	AVG_CNT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RANGE_MODE [23:22]		None [21:21]	SHIFT_R [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						TR_DONE_GRP_VIO [25:25]	None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	POST_PROC	RW	RW	Undefined	Post processing
	NONE			0	No postprocessing
	AVG			1	Averaging
	AVG_RANGE			2	Averaging followed by Range detect
	RANGE			3	Range detect
	RANGE_PULSE			4	Range detect followed by pulse detect
	RESERVED0			5	N/A
	RESERVED1			6	N/A
	RESERVED2			7	N/A
6	LEFT_ALIGN	RW	RW	Undefined	Left or right align data in result[15:0]. 0: the data is right aligned in result[11:0], with sign extension to 16 bits if enabled 1: the data is left aligned in result[15:4] with the lower nibble 0. Caveat if the result was more than 12 bits (e.g. after averaging) then the bits above 12 will be discarded.
7	SIGN_EXT	RW	RW	Undefined	Output data is sign extended
	UNSIGNED			0	Default: result data is unsigned (zero extended if needed)
	SIGNED			1	Result data is signed (sign extended if needed)

Bits	Name	SW	HW	Default or Enum	Description
8:15	AVG_CNT	RW	RW	Undefined	Either averaging count (minus 1) or Pulse positive reload value Averaging Count for channels that have averaging enabled. A channel will be sampled (AVG_CNT+1) = [1..256] times. The signal will be acquired back to back (1st order accumulate and dump filter), the average result is calculated and stored and then the next enabled channel is sampled. If more than 16 sample are taken (AVG_CNT>=16) then AVG_SHIFT must be set so that the result after shifting fits in 16 bits Pulse detect positive reload value PULSE_POS_RL[7:0]
16:20	SHIFT_R	RW	RW	Undefined	Either Shift Right (no pulse detection) or Pulse negative reload value (if pulse detection is enabled) Shift right SHIFT_R[3:0] = [0..12]: the result (typically after averaging) is shifted right as specified here. Software has to make sure that the result fits in less than 16 bits. Any value >12 will be treated as 12, bit [4] is always ignored. This can also be used to fit the 12-bit result in 8 bits. Pulse detect negative reload value PULSE_NEG_RL[4:0]
22:23	RANGE_MODE	RW	RW	Undefined	Range detect mode
	BELOW_LO			0	Below Low threshold (result < Lo)
	INSIDE_RANGE			1	Inside range (Lo <= result < Hi)
	ABOVE_HI			2	Above high threshold (Hi <= result)
	OUTSIDE_RANGE			3	Outside range (result < Lo Hi <= result)
25	TR_DONE_GRP_VIO	RW	RW	Undefined	Select tr_sar_ch_done mode for last channel of a group, ignored for all other channels Also see TR_CTL.DONE_LEVEL
	DONE			0	Default: tr_sar_ch_done is set when the group is done
	GRP_RANGE_VIO			1	tr_sar_ch_done is only set if any of the channels in the group has a Range Violation. This mode is ignored if this is not the last channel in the group. Note that if none of the channels in the group have Range detection enabled then the trigger will never get set.

19.5.1.18.4 PASS_SAR_CH_RANGE_CTL

Description: Range thresholds
Address: 0x4090080C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Make sure the channel or the IP is disabled before changing this register
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RANGE_LO [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RANGE_LO [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RANGE_HI [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RANGE_HI [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RANGE_LO	RW	RW	Undefined	Range detect low threshold (Lo)
16:31	RANGE_HI	RW	RW	Undefined	Range detect high threshold (Hi)

19.5.1.18.5 PASS_SAR_CH_INTR

Description: Interrupt request register.
Address: 0x40900810
Offset: 0x10
Retention: Not Retained
IsDeepSleep: No
Comment: interrupts for one channel
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					GRP_OVERFLOW [2:2]	GRP_CANCELLED [1:1]	GRP_DONE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CH_OVERFLOW [10:10]	CH_PULSE [9:9]	CH_RANGE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GRP_DONE	RW1C	RW1C	0	Done Interrupt: hardware sets this interrupt for the last channel of a group if the group scan is done. Write with '1' to clear bit.
1	GRP_CANCELLED	RW1C	RW1C	0	Cancelled Interrupt: hardware sets this interrupt for the last channel of a group if the group scan was preempted and CANCELLED. Note that it is possible that also the GRP_DONE interrupt is set. If that is the case one or more new triggers were detected while the group was already busy, i.e. triggers are too fast. Write with '1' to clear bit.
2	GRP_OVERFLOW	RW1C	RW1C	0	Overflow Interrupt: hardware sets this interrupt for the last channel of a group if the group scan is done and the Done interrupt is already (still) pending. Write with '1' to clear bit.
8	CH_RANGE	RW1C	RW1C	0	Range detect Interrupt: hardware sets this interrupt for each channel if the conversion result (after averaging) of that channel met the condition specified by the SAR_RANGE registers. This interrupt is mutual exclusive with Pulse detect interrupt. Write with '1' to clear bit.
9	CH_PULSE	RW1C	RW1C	0	Pulse detect Interrupt: hardware sets this interrupt for each channel if the positive pulse counter reaches zero. This interrupt is mutual exclusive with Range detect interrupt. Write with '1' to clear bit.
10	CH_OVERFLOW	RW1C	RW1C	0	Channel overflow Interrupt: hardware sets this interrupt for each channel if a new Pulse or Range interrupt is detected while the interrupt is still pending or when DW did not acknowledge data pickup. Write with '1' to clear bit.

19.5.1.18.6 PASS_SAR_CH_INTR_SET

Description: Interrupt set request register
Address: 0x40900814
Offset: 0x14
Retention: Not Retained
IsDeepSleep: No
Comment: Not really a register, intended for verification/debug. When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					GRP_OVERFLOW_SET [2:2]	GRP_CANCELLED_SET [1:1]	GRP_DONE_SET [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CH_OVERFLOW_SET [10:10]	CH_PULSE_SET [9:9]	CH_RANGE_SET [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GRP_DONE_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	GRP_CANCELLED_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	GRP_OVERFLOW_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	CH_RANGE_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
9	CH_PULSE_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
10	CH_OVERFLOW_SET	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

19.5.1.18.7 PASS_SAR_CH_INTR_MASK

Description: Interrupt mask register.
Address: 0x40900818
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					GRP_OVERFLOW_MASK [2:2]	GRP_CANCELLED_MASK [1:1]	GRP_DONE_MASK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CH_OVERFLOW_MASK [10:10]	CH_PULSE_MASK [9:9]	CH_RANGE_MASK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GRP_DONE_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	GRP_CANCELLED_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	GRP_OVERFLOW_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	CH_RANGE_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
9	CH_PULSE_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
10	CH_OVERFLOW_MASK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

19.5.1.18.8 PASS_SAR_CH_INTR_MASKED

Description: Interrupt masked request register
Address: 0x4090081C
Offset: 0x1C
Retention: Not Retained
IsDeepSleep: No
Comment: If the value is not zero then the SAR interrupt signal to the NVIC is high. When read, this register reflects a bitwise AND between the interrupt request and mask registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					GRP_OVERFLOW_MASKED [2:2]	GRP_CANCELLED_MASKED [1:1]	GRP_DONE_MASKED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CH_OVERFLOW_MASKED [10:10]	CH_PULSE_MASKED [9:9]	CH_RANGE_MASKED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GRP_DONE_MASKED	R	R	0	Logical and of corresponding request and mask bits.
1	GRP_CANCELLED_MASKED	R	R	0	Logical and of corresponding request and mask bits.
2	GRP_OVERFLOW_MASKED	R	R	0	Logical and of corresponding request and mask bits.
8	CH_RANGE_MASKED	R	R	0	Logical and of corresponding request and mask bits.
9	CH_PULSE_MASKED	R	R	0	Logical and of corresponding request and mask bits.
10	CH_OVERFLOW_MASKED	R	R	0	Logical and of corresponding request and mask bits.

19.5.1.18.9 PASS_SAR_CH_WORK

Description: Working data register
Address: 0x40900820
Offset: 0x20
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORK [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	WORK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID_MIR [31:31]	PULSE_MIR [30:30]	RANGE_MIR [29:29]	ABOVE_HI_MIR [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	WORK	R	R	Undefined	SAR conversion working data of the channel. The data is written here right after sampling this channel.
28	ABOVE_HI_MIR	R	R	0	mirror bit of the corresponding ABOVE_HI bit
29	RANGE_MIR	R	R	0	mirror bit of corresponding bit in WORK_RANGE register
30	PULSE_MIR	R	R	0	mirror bit of corresponding bit in WORK_PULSE register
31	VALID_MIR	R	R	0	mirror bit of corresponding bit in WORK_VALID register

19.5.1.18.10 PASS_SAR_CH_RESULT

Description: Result data register
Address: 0x40900824
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESULT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESULT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID_MIR [31:31]	PULSE_INTR_MIR [30:30]	RANGE_INTR_MIR [29:29]	ABOVE_HI_MIR [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RESULT	R	R	Undefined	SAR conversion result of the channel. The data is copied here from the WORK field after all enabled channels in this scan have been sampled.
28	ABOVE_HI_MIR	R	R	0	mirror bit of the corresponding ABOVE_HI bit
29	RANGE_INTR_MIR	R	R	0	mirror bit of INTR.CH_RANGE bit
30	PULSE_INTR_MIR	R	R	0	mirror bit of INTR.CH_PULSE bit
31	VALID_MIR	R	R	0	mirror bit of the corresponding bit in RESULT_VALID register

19.5.1.18.11 PASS_SAR_CH_GRP_STAT

Description: Group status register
Address: 0x40900828
Offset: 0x28
Retention: Not Retained
IsDeepSleep: No
Comment: This register contains the status information required for a coherent read for the AutoSAR 'ADC Channel Group Status Service'
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					GRP_OVERFLOW [2:2]	GRP_CANCELLED [1:1]	GRP_COMPLETE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CH_OVERFLOW [10:10]	CH_PULSE_COMPLETE [9:9]	CH_RANGE_COMPLETE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							GRP_BUSY [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GRP_COMPLETE	R	R	0	Group acquisition complete. This is a copy of the INTR.GRP_DONE bit.
1	GRP_CANCELLED	R	R	0	Group Cancelled. This is a copy of the INTR.GRP_CANCELLED bit.
2	GRP_OVERFLOW	R	R	0	Group Overflow. This is a copy of the INTR.GRP_OVERFLOW bit.
8	CH_RANGE_COMPLETE	R	R	0	Channel Range complete. This is a copy of the INTR.CH_RANGE bit.
9	CH_PULSE_COMPLETE	R	R	0	Channel Pulse complete. This is a copy of the INTR.CH_PULSE bit.
10	CH_OVERFLOW	R	R	0	Channel Overflow. This is a copy of the INTR.CH_OVERFLOW bit.
16	GRP_BUSY	R	R	0	Group acquisition busy. This is a copy of the TR_PENDING bit of the first channel of the group.

19.5.1.18.12 PASS_SAR_CH_ENABLE

Description: Enable register
Address: 0x40900838
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							CHAN_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CHAN_EN	RW	RW	0	Channel enable. - 0: the corresponding channel is disabled. Corresponding trigger will be reset immediately. - 1: the corresponding channel is enabled. Note: To disable a group either stop the trigger first or begin with disabling the lowest channel first. To enable a group either start with enabling the last channel first and the first channel last, or start the trigger after all channels are enabled. If these rules are not followed the result is undefined.

19.5.1.18.13 PASS_SAR_CH_TR_CMD

Description: Software triggers
Address: 0x4090083C
Offset: 0x3C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	START	RW1S	RW1S	0	Software start trigger. When written with '1', a start trigger is generated which sets the corresponding TR_PEND bit (only if the channel is enabled). A read always returns a 0.

19.5.2 EPASS_MMIO

19.5.2.1 PASS_PASS_CTL

Description: PASS control register
Address: 0x409F0000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		SUPPLY_MON_LVL_B [5:5]	SUPPLY_MON_EN_B [4:4]	None [3:2]		SUPPLY_MON_LVL_A [1:1]	SUPPLY_MON_EN_A [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	REFBUF_MODE [22:21]		None [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	DBG_FREEZE_EN [31:28]				None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SUPPLY_MON_EN_A	RW	RW	0	Supply monitor enable for AMUXBUS_A (amuxbus_a_mon)
1	SUPPLY_MON_LVL_A	RW	RW	0	Supply monitor level select for AMUXBUS_A
	VRL			0	amuxbus_a_mon = VRL
	VRH			1	amuxbus_a_mon = VRH
4	SUPPLY_MON_EN_B	RW	RW	0	Supply monitor enable for AMUXBUS_B (amuxbus_b_mon)
5	SUPPLY_MON_LVL_B	RW	RW	0	Supply monitor level select for AMUXBUS_B
	VRL			0	amuxbus_b_mon = VRL
	VRH			1	amuxbus_b_mon = VRH
21:22	REFBUF_MODE	RW	RW	0	Reference mode. The reference needs to be present when using TEMP sensor or diagnostic reference (in addition to SAR.DIAG_CTL.DIAG_EN). Note that setting this mode is not required for the ADC operation itself.
	OFF			0	No reference
	ON			1	Reference = buffered Vbg from SRSS
	RESERVED			2	undefined
	BYPASS			3	Reference = unbuffered Vbg from SRSS
28:31	DBG_FREEZE_EN	RW	RW	0	Debug pause enable, 1 per ADC. When set a high tr_debug_freeze trigger will prevent the scheduler from starting acquisitions on a new channel. Note that averaging for an already started channel will be completed.

19.5.2.2 PASS_SAR_TR_IN_SEL

Description: per SAR generic input trigger select
Address: 0x409F0020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: forward 5 out of max 16 generic input triggers to one SAR instance (there are 5 generic input triggers per SAR)
Default: 0x43210

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IN1_SEL [7:4]				IN0_SEL [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	IN3_SEL [15:12]				IN2_SEL [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				IN4_SEL [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	IN0_SEL	RW	RW	0	Select generic trigger for SAR generic trigger input 0
4:7	IN1_SEL	RW	RW	1	Select generic trigger for SAR generic trigger input 1
8:11	IN2_SEL	RW	RW	2	Select generic trigger for SAR generic trigger input 2
12:15	IN3_SEL	RW	RW	3	Select generic trigger for SAR generic trigger input 3
16:19	IN4_SEL	RW	RW	4	Select generic trigger for SAR generic trigger input 4

19.5.2.3 PASS_SAR_TR_OUT_SEL

Description: per SAR generic output trigger select
Address: 0x409F0040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: forward 2 of the up to 64 SAR triggers (tr_sar_ch_done + tr_sar_ch_rangevio) to a generic output trigger
Default: 0x100

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		OUT0_SEL [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		OUT1_SEL [13:8]					

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	OUT0_SEL	RW	RW	0	Select SAR output trigger for generic trigger output 0 0-31: selects a tr_sar_ch_done trigger 32-63: selects a tr_sar_ch_rangvio trigger
8:13	OUT1_SEL	RW	RW	1	Select SAR output trigger for generic trigger output 1

20 PERI

Description Peripheral interconnect
Base Address 0x40000000
Size 0x10000
Slave Num MMIO0 - 0

Register Name	Address	Permission	Description
PERI_TIMEOUT_CTL	0x40000200	FULL	Timeout control
PERI_TR_CMD	0x40000220	FULL	Trigger command
PERI_ECC_CTL	0x40002000	FULL	ECC control

20.1 GR 0

Register Name	Address	Permission	Description
PERI_GR0_SL_CTL	0x40004010	FULL	Slave control Note:ENABLED_3 ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.2 GR 1

Register Name	Address	Permission	Description
PERI_GR1_SL_CTL	0x40004050	FULL	Slave control Note:ENABLED_1 ENABLED_2 ENABLED_3 ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.3 GR 2

Register Name	Address	Permission	Description
PERI_GR2_SL_CTL	0x40004090	FULL	Slave control Note:ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.4 GR 3

Register Name	Address	Permission	Description
PERI_GR3_CLOCK_CTL	0x400040C0	FULL	Clock control
PERI_GR3_SL_CTL	0x400040D0	FULL	Slave control Note:ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.5 GR 4

Register Name	Address	Permission	Description
PERI_GR4_CLOCK_CTL	0x40004100	FULL	Clock control
PERI_GR4_SL_CTL	0x40004110	FULL	Slave control Note:ENABLED_3 ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.6 GR 5

Register Name	Address	Permission	Description
PERI_GR5_CLOCK_CTL	0x40004140	FULL	Clock control

Register Name	Address	Permission	Description
PERI_GR5_SL_CTL	0x40004150	FULL	Slave control Note:ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.7 GR 6

Register Name	Address	Permission	Description
PERI_GR6_CLOCK_CTL	0x40004180	FULL	Clock control
PERI_GR6_SL_CTL	0x40004190	FULL	Slave control Note:ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.8 GR 8

Register Name	Address	Permission	Description
PERI_GR8_CLOCK_CTL	0x40004200	FULL	Clock control
PERI_GR8_SL_CTL	0x40004210	FULL	Slave control Note:ENABLED_3 ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.9 GR 9

Register Name	Address	Permission	Description
PERI_GR9_CLOCK_CTL	0x40004240	FULL	Clock control
PERI_GR9_SL_CTL	0x40004250	FULL	Slave control Note:ENABLED_1 ENABLED_2 ENABLED_3 ENABLED_4 ENABLED_5 ENABLED_6 ENABLED_7 ENABLED_8 ENABLED_9 ENABLED_10 ENABLED_11 ENABLED_12 ENABLED_13 ENABLED_14 ENABLED_15 are not available for this register

20.10 TR_GR 0

Register Name	Address	Permission	Description
PERI_TR_GR0_TR_CTL0	0x40008000	FULL	Trigger control register
PERI_TR_GR0_TR_CTL1	0x40008004	FULL	Trigger control register
PERI_TR_GR0_TR_CTL2	0x40008008	FULL	Trigger control register
PERI_TR_GR0_TR_CTL3	0x4000800C	FULL	Trigger control register
PERI_TR_GR0_TR_CTL4	0x40008010	FULL	Trigger control register
PERI_TR_GR0_TR_CTL5	0x40008014	FULL	Trigger control register
PERI_TR_GR0_TR_CTL6	0x40008018	FULL	Trigger control register
PERI_TR_GR0_TR_CTL7	0x4000801C	FULL	Trigger control register

20.11 TR_GR 1

Register Name	Address	Permission	Description
PERI_TR_GR1_TR_CTL0	0x40008400	FULL	Trigger control register
PERI_TR_GR1_TR_CTL1	0x40008404	FULL	Trigger control register
PERI_TR_GR1_TR_CTL2	0x40008408	FULL	Trigger control register
PERI_TR_GR1_TR_CTL3	0x4000840C	FULL	Trigger control register
PERI_TR_GR1_TR_CTL4	0x40008410	FULL	Trigger control register
PERI_TR_GR1_TR_CTL5	0x40008414	FULL	Trigger control register
PERI_TR_GR1_TR_CTL6	0x40008418	FULL	Trigger control register
PERI_TR_GR1_TR_CTL7	0x4000841C	FULL	Trigger control register

20.12 TR_GR 2

Register Name	Address	Permission	Description
PERI_TR_GR2_TR_CTL0	0x40008800	FULL	Trigger control register
PERI_TR_GR2_TR_CTL1	0x40008804	FULL	Trigger control register
PERI_TR_GR2_TR_CTL2	0x40008808	FULL	Trigger control register

Register Name	Address	Permission	Description
PERI_TR_GR2_TR_CTL3	0x4000880C	FULL	Trigger control register
PERI_TR_GR2_TR_CTL4	0x40008810	FULL	Trigger control register
PERI_TR_GR2_TR_CTL5	0x40008814	FULL	Trigger control register
PERI_TR_GR2_TR_CTL6	0x40008818	FULL	Trigger control register
PERI_TR_GR2_TR_CTL7	0x4000881C	FULL	Trigger control register
PERI_TR_GR2_TR_CTL8	0x40008820	FULL	Trigger control register
PERI_TR_GR2_TR_CTL9	0x40008824	FULL	Trigger control register
PERI_TR_GR2_TR_CTL10	0x40008828	FULL	Trigger control register
PERI_TR_GR2_TR_CTL11	0x4000882C	FULL	Trigger control register
PERI_TR_GR2_TR_CTL12	0x40008830	FULL	Trigger control register
PERI_TR_GR2_TR_CTL13	0x40008834	FULL	Trigger control register
PERI_TR_GR2_TR_CTL14	0x40008838	FULL	Trigger control register
PERI_TR_GR2_TR_CTL15	0x4000883C	FULL	Trigger control register

20.13 TR_GR 3

Register Name	Address	Permission	Description
PERI_TR_GR3_TR_CTL0	0x40008C00	FULL	Trigger control register
PERI_TR_GR3_TR_CTL1	0x40008C04	FULL	Trigger control register
PERI_TR_GR3_TR_CTL2	0x40008C08	FULL	Trigger control register
PERI_TR_GR3_TR_CTL3	0x40008C0C	FULL	Trigger control register
PERI_TR_GR3_TR_CTL4	0x40008C10	FULL	Trigger control register
PERI_TR_GR3_TR_CTL5	0x40008C14	FULL	Trigger control register
PERI_TR_GR3_TR_CTL6	0x40008C18	FULL	Trigger control register
PERI_TR_GR3_TR_CTL7	0x40008C1C	FULL	Trigger control register

20.14 TR_GR 4

Register Name	Address	Permission	Description
PERI_TR_GR4_TR_CTL0	0x40009000	FULL	Trigger control register

20.15 TR_GR 5

Register Name	Address	Permission	Description
PERI_TR_GR5_TR_CTL0	0x40009400	FULL	Trigger control register
PERI_TR_GR5_TR_CTL1	0x40009404	FULL	Trigger control register
PERI_TR_GR5_TR_CTL2	0x40009408	FULL	Trigger control register
PERI_TR_GR5_TR_CTL3	0x4000940C	FULL	Trigger control register
PERI_TR_GR5_TR_CTL4	0x40009410	FULL	Trigger control register
PERI_TR_GR5_TR_CTL5	0x40009414	FULL	Trigger control register
PERI_TR_GR5_TR_CTL6	0x40009418	FULL	Trigger control register
PERI_TR_GR5_TR_CTL7	0x4000941C	FULL	Trigger control register
PERI_TR_GR5_TR_CTL8	0x40009420	FULL	Trigger control register
PERI_TR_GR5_TR_CTL9	0x40009424	FULL	Trigger control register
PERI_TR_GR5_TR_CTL10	0x40009428	FULL	Trigger control register
PERI_TR_GR5_TR_CTL11	0x4000942C	FULL	Trigger control register

20.16 TR_GR 6

Register Name	Address	Permission	Description
PERI_TR_GR6_TR_CTL0	0x40009800	FULL	Trigger control register
PERI_TR_GR6_TR_CTL1	0x40009804	FULL	Trigger control register
PERI_TR_GR6_TR_CTL2	0x40009808	FULL	Trigger control register
PERI_TR_GR6_TR_CTL3	0x4000980C	FULL	Trigger control register
PERI_TR_GR6_TR_CTL4	0x40009810	FULL	Trigger control register
PERI_TR_GR6_TR_CTL5	0x40009814	FULL	Trigger control register
PERI_TR_GR6_TR_CTL6	0x40009818	FULL	Trigger control register
PERI_TR_GR6_TR_CTL7	0x4000981C	FULL	Trigger control register
PERI_TR_GR6_TR_CTL8	0x40009820	FULL	Trigger control register
PERI_TR_GR6_TR_CTL9	0x40009824	FULL	Trigger control register
PERI_TR_GR6_TR_CTL10	0x40009828	FULL	Trigger control register
PERI_TR_GR6_TR_CTL11	0x4000982C	FULL	Trigger control register
PERI_TR_GR6_TR_CTL12	0x40009830	FULL	Trigger control register
PERI_TR_GR6_TR_CTL13	0x40009834	FULL	Trigger control register
PERI_TR_GR6_TR_CTL14	0x40009838	FULL	Trigger control register

20.17 TR_GR 7

Register Name	Address	Permission	Description
PERI_TR_GR7_TR_CTL0	0x40009C00	FULL	Trigger control register
PERI_TR_GR7_TR_CTL1	0x40009C04	FULL	Trigger control register
PERI_TR_GR7_TR_CTL2	0x40009C08	FULL	Trigger control register
PERI_TR_GR7_TR_CTL3	0x40009C0C	FULL	Trigger control register
PERI_TR_GR7_TR_CTL4	0x40009C10	FULL	Trigger control register
PERI_TR_GR7_TR_CTL5	0x40009C14	FULL	Trigger control register
PERI_TR_GR7_TR_CTL6	0x40009C18	FULL	Trigger control register
PERI_TR_GR7_TR_CTL7	0x40009C1C	FULL	Trigger control register
PERI_TR_GR7_TR_CTL8	0x40009C20	FULL	Trigger control register
PERI_TR_GR7_TR_CTL9	0x40009C24	FULL	Trigger control register
PERI_TR_GR7_TR_CTL10	0x40009C28	FULL	Trigger control register
PERI_TR_GR7_TR_CTL11	0x40009C2C	FULL	Trigger control register

20.18 TR_GR 8

Register Name	Address	Permission	Description
PERI_TR_GR8_TR_CTL0	0x4000A000	FULL	Trigger control register
PERI_TR_GR8_TR_CTL1	0x4000A004	FULL	Trigger control register
PERI_TR_GR8_TR_CTL2	0x4000A008	FULL	Trigger control register
PERI_TR_GR8_TR_CTL3	0x4000A00C	FULL	Trigger control register
PERI_TR_GR8_TR_CTL4	0x4000A010	FULL	Trigger control register
PERI_TR_GR8_TR_CTL5	0x4000A014	FULL	Trigger control register
PERI_TR_GR8_TR_CTL6	0x4000A018	FULL	Trigger control register
PERI_TR_GR8_TR_CTL7	0x4000A01C	FULL	Trigger control register

20.19 TR_GR 9

Register Name	Address	Permission	Description
PERI_TR_GR9_TR_CTL0	0x4000A400	FULL	Trigger control register
PERI_TR_GR9_TR_CTL1	0x4000A404	FULL	Trigger control register
PERI_TR_GR9_TR_CTL2	0x4000A408	FULL	Trigger control register
PERI_TR_GR9_TR_CTL3	0x4000A40C	FULL	Trigger control register
PERI_TR_GR9_TR_CTL4	0x4000A410	FULL	Trigger control register
PERI_TR_GR9_TR_CTL5	0x4000A414	FULL	Trigger control register
PERI_TR_GR9_TR_CTL6	0x4000A418	FULL	Trigger control register
PERI_TR_GR9_TR_CTL7	0x4000A41C	FULL	Trigger control register
PERI_TR_GR9_TR_CTL8	0x4000A420	FULL	Trigger control register
PERI_TR_GR9_TR_CTL9	0x4000A424	FULL	Trigger control register
PERI_TR_GR9_TR_CTL10	0x4000A428	FULL	Trigger control register

20.20 TR_GR 10

Register Name	Address	Permission	Description
PERI_TR_GR10_TR_CTL0	0x4000A800	FULL	Trigger control register Note: TR_INV TR_EDGE are not available for this register
PERI_TR_GR10_TR_CTL1	0x4000A804	FULL	Trigger control register
PERI_TR_GR10_TR_CTL2	0x4000A808	FULL	Trigger control register
PERI_TR_GR10_TR_CTL3	0x4000A80C	FULL	Trigger control register
PERI_TR_GR10_TR_CTL4	0x4000A810	FULL	Trigger control register

20.21 TR_GR 11

Register Name	Address	Permission	Description
PERI_TR_GR11_TR_CTL0	0x4000AC00	FULL	Trigger control register Note: TR_INV TR_EDGE are not available for this register
PERI_TR_GR11_TR_CTL1	0x4000AC04	FULL	Trigger control register
PERI_TR_GR11_TR_CTL2	0x4000AC08	FULL	Trigger control register
PERI_TR_GR11_TR_CTL3	0x4000AC0C	FULL	Trigger control register
PERI_TR_GR11_TR_CTL4	0x4000AC10	FULL	Trigger control register

20.22 TR_GR 12

Register Name	Address	Permission	Description
PERI_TR_GR12_TR_CTL0	0x4000B000	FULL	Trigger control register Note: TR_INV TR_EDGE are not available for this register
PERI_TR_GR12_TR_CTL1	0x4000B004	FULL	Trigger control register
PERI_TR_GR12_TR_CTL2	0x4000B008	FULL	Trigger control register
PERI_TR_GR12_TR_CTL3	0x4000B00C	FULL	Trigger control register
PERI_TR_GR12_TR_CTL4	0x4000B010	FULL	Trigger control register

20.23 TR_1TO1_GR 0

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR0_TR_CTL0	0x4000C000	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL1	0x4000C004	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL2	0x4000C008	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL3	0x4000C00C	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL4	0x4000C010	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL5	0x4000C014	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL6	0x4000C018	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL7	0x4000C01C	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL8	0x4000C020	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL9	0x4000C024	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL10	0x4000C028	FULL	Trigger control register
PERI_TR_1TO1_GR0_TR_CTL11	0x4000C02C	FULL	Trigger control register

20.24 TR_1TO1_GR 1

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR1_TR_CTL0	0x4000C400	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL1	0x4000C404	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL2	0x4000C408	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL3	0x4000C40C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL4	0x4000C410	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL5	0x4000C414	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL6	0x4000C418	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL7	0x4000C41C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL8	0x4000C420	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL9	0x4000C424	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL10	0x4000C428	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL11	0x4000C42C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL12	0x4000C430	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL13	0x4000C434	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL14	0x4000C438	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL15	0x4000C43C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL16	0x4000C440	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL17	0x4000C444	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL18	0x4000C448	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL19	0x4000C44C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL20	0x4000C450	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL21	0x4000C454	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL22	0x4000C458	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL23	0x4000C45C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL24	0x4000C460	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL25	0x4000C464	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL26	0x4000C468	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL27	0x4000C46C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL28	0x4000C470	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL29	0x4000C474	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL30	0x4000C478	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL31	0x4000C47C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL32	0x4000C480	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL33	0x4000C484	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL34	0x4000C488	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL35	0x4000C48C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL36	0x4000C490	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL37	0x4000C494	FULL	Trigger control register

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR1_TR_CTL38	0x4000C498	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL39	0x4000C49C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL40	0x4000C4A0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL41	0x4000C4A4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL42	0x4000C4A8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL43	0x4000C4AC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL44	0x4000C4B0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL45	0x4000C4B4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL46	0x4000C4B8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL47	0x4000C4BC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL48	0x4000C4C0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL49	0x4000C4C4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL50	0x4000C4C8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL51	0x4000C4CC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL52	0x4000C4D0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL53	0x4000C4D4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL54	0x4000C4D8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL55	0x4000C4DC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL56	0x4000C4E0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL57	0x4000C4E4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL58	0x4000C4E8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL59	0x4000C4EC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL60	0x4000C4F0	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL61	0x4000C4F4	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL62	0x4000C4F8	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL63	0x4000C4FC	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL64	0x4000C500	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL65	0x4000C504	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL66	0x4000C508	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL67	0x4000C50C	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL68	0x4000C510	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL69	0x4000C514	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL70	0x4000C518	FULL	Trigger control register
PERI_TR_1TO1_GR1_TR_CTL71	0x4000C51C	FULL	Trigger control register

20.25 TR_1TO1_GR 2

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR2_TR_CTL0	0x4000C800	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL1	0x4000C804	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL2	0x4000C808	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL3	0x4000C80C	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL4	0x4000C810	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL5	0x4000C814	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL6	0x4000C818	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL7	0x4000C81C	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL8	0x4000C820	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL9	0x4000C824	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL10	0x4000C828	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL11	0x4000C82C	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL12	0x4000C830	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL13	0x4000C834	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL14	0x4000C838	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL15	0x4000C83C	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL16	0x4000C840	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL17	0x4000C844	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL18	0x4000C848	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL19	0x4000C84C	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL20	0x4000C850	FULL	Trigger control register
PERI_TR_1TO1_GR2_TR_CTL21	0x4000C854	FULL	Trigger control register

20.26 TR_1TO1_GR 3

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR3_TR_CTL0	0x4000CC00	FULL	Trigger control register
PERI_TR_1TO1_GR3_TR_CTL1	0x4000CC04	FULL	Trigger control register

20.27 TR_1TO1_GR 4

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR4_TR_CTL0	0x4000D000	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL1	0x4000D004	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL2	0x4000D008	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL3	0x4000D00C	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL4	0x4000D010	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL5	0x4000D014	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL6	0x4000D018	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL7	0x4000D01C	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL8	0x4000D020	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL9	0x4000D024	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL10	0x4000D028	FULL	Trigger control register
PERI_TR_1TO1_GR4_TR_CTL11	0x4000D02C	FULL	Trigger control register

20.28 TR_1TO1_GR 5

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR5_TR_CTL0	0x4000D400	FULL	Trigger control register
PERI_TR_1TO1_GR5_TR_CTL1	0x4000D404	FULL	Trigger control register
PERI_TR_1TO1_GR5_TR_CTL2	0x4000D408	FULL	Trigger control register
PERI_TR_1TO1_GR5_TR_CTL3	0x4000D40C	FULL	Trigger control register
PERI_TR_1TO1_GR5_TR_CTL4	0x4000D410	FULL	Trigger control register
PERI_TR_1TO1_GR5_TR_CTL5	0x4000D414	FULL	Trigger control register

20.29 TR_1TO1_GR 6

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR6_TR_CTL0	0x4000D800	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL1	0x4000D804	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL2	0x4000D808	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL3	0x4000D80C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL4	0x4000D810	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL5	0x4000D814	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL6	0x4000D818	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL7	0x4000D81C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL8	0x4000D820	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL9	0x4000D824	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL10	0x4000D828	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL11	0x4000D82C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL12	0x4000D830	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL13	0x4000D834	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL14	0x4000D838	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL15	0x4000D83C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL16	0x4000D840	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL17	0x4000D844	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL18	0x4000D848	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL19	0x4000D84C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL20	0x4000D850	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL21	0x4000D854	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL22	0x4000D858	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL23	0x4000D85C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL24	0x4000D860	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL25	0x4000D864	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL26	0x4000D868	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL27	0x4000D86C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL28	0x4000D870	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL29	0x4000D874	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL30	0x4000D878	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL31	0x4000D87C	FULL	Trigger control register

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR6_TR_CTL32	0x4000D880	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL33	0x4000D884	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL34	0x4000D888	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL35	0x4000D88C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL36	0x4000D890	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL37	0x4000D894	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL38	0x4000D898	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL39	0x4000D89C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL40	0x4000D8A0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL41	0x4000D8A4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL42	0x4000D8A8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL43	0x4000D8AC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL44	0x4000D8B0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL45	0x4000D8B4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL46	0x4000D8B8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL47	0x4000D8BC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL48	0x4000D8C0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL49	0x4000D8C4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL50	0x4000D8C8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL51	0x4000D8CC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL52	0x4000D8D0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL53	0x4000D8D4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL54	0x4000D8D8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL55	0x4000D8DC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL56	0x4000D8E0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL57	0x4000D8E4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL58	0x4000D8E8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL59	0x4000D8EC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL60	0x4000D8F0	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL61	0x4000D8F4	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL62	0x4000D8F8	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL63	0x4000D8FC	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL64	0x4000D900	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL65	0x4000D904	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL66	0x4000D908	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL67	0x4000D90C	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL68	0x4000D910	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL69	0x4000D914	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL70	0x4000D918	FULL	Trigger control register
PERI_TR_1TO1_GR6_TR_CTL71	0x4000D91C	FULL	Trigger control register

20.30 TR_1TO1_GR 7

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR7_TR_CTL0	0x4000DC00	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL1	0x4000DC04	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL2	0x4000DC08	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL3	0x4000DC0C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL4	0x4000DC10	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL5	0x4000DC14	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL6	0x4000DC18	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL7	0x4000DC1C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL8	0x4000DC20	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL9	0x4000DC24	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL10	0x4000DC28	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL11	0x4000DC2C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL12	0x4000DC30	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL13	0x4000DC34	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL14	0x4000DC38	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL15	0x4000DC3C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL16	0x4000DC40	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL17	0x4000DC44	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL18	0x4000DC48	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL19	0x4000DC4C	FULL	Trigger control register

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR7_TR_CTL20	0x4000DC50	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL21	0x4000DC54	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL22	0x4000DC58	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL23	0x4000DC5C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL24	0x4000DC60	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL25	0x4000DC64	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL26	0x4000DC68	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL27	0x4000DC6C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL28	0x4000DC70	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL29	0x4000DC74	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL30	0x4000DC78	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL31	0x4000DC7C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL32	0x4000DC80	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL33	0x4000DC84	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL34	0x4000DC88	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL35	0x4000DC8C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL36	0x4000DC90	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL37	0x4000DC94	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL38	0x4000DC98	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL39	0x4000DC9C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL40	0x4000DCA0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL41	0x4000DCA4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL42	0x4000DCA8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL43	0x4000DCAC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL44	0x4000DCB0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL45	0x4000DCB4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL46	0x4000DCB8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL47	0x4000DCBC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL48	0x4000DCC0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL49	0x4000DCC4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL50	0x4000DCC8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL51	0x4000DCCC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL52	0x4000DCD0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL53	0x4000DCD4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL54	0x4000DCD8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL55	0x4000DCDC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL56	0x4000DCE0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL57	0x4000DCE4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL58	0x4000DCE8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL59	0x4000DCEC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL60	0x4000DCF0	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL61	0x4000DCF4	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL62	0x4000DCF8	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL63	0x4000DCFC	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL64	0x4000DD00	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL65	0x4000DD04	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL66	0x4000DD08	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL67	0x4000DD0C	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL68	0x4000DD10	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL69	0x4000DD14	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL70	0x4000DD18	FULL	Trigger control register
PERI_TR_1TO1_GR7_TR_CTL71	0x4000DD1C	FULL	Trigger control register

20.31 TR_1TO1_GR 8

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR8_TR_CTL0	0x4000E000	FULL	Trigger control register
PERI_TR_1TO1_GR8_TR_CTL1	0x4000E004	FULL	Trigger control register
PERI_TR_1TO1_GR8_TR_CTL2	0x4000E008	FULL	Trigger control register
PERI_TR_1TO1_GR8_TR_CTL3	0x4000E00C	FULL	Trigger control register

20.32 TR_1TO1_GR 9

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR9_TR_CTL0	0x4000E400	FULL	Trigger control register
PERI_TR_1TO1_GR9_TR_CTL1	0x4000E404	FULL	Trigger control register
PERI_TR_1TO1_GR9_TR_CTL2	0x4000E408	FULL	Trigger control register
PERI_TR_1TO1_GR9_TR_CTL3	0x4000E40C	FULL	Trigger control register

20.33 TR_1TO1_GR 10

Register Name	Address	Permission	Description
PERI_TR_1TO1_GR10_TR_CTL0	0x4000E800	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL1	0x4000E804	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL2	0x4000E808	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL3	0x4000E80C	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL4	0x4000E810	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL5	0x4000E814	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL6	0x4000E818	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL7	0x4000E81C	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL8	0x4000E820	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL9	0x4000E824	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL10	0x4000E828	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL11	0x4000E82C	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL12	0x4000E830	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL13	0x4000E834	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL14	0x4000E838	FULL	Trigger control register
PERI_TR_1TO1_GR10_TR_CTL15	0x4000E83C	FULL	Trigger control register

20.34 Register Details

20.34.1 PERI_TIMEOUT_CTL

Description: Timeout control

Address: 0x40000200

Offset: 0x200

Retention: Retained

IsDeepSleep: No

Comment: The presence of the TIMEOUT_CTL register is dependent on the TIMEOUT_PRESENT parameter.

The presence of TIMEOUT_CTL requires slave 0 of the peripheral group to be present (SL0_PRESENT must be '1').

Default: 0xFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TIMEOUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	TIMEOUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	TIMEOUT	RW	RW	65535	This field specifies a number of clock cycles (clk_slow). If an AHB-Lite bus transfer takes more than the specified number of cycles (timeout detection), the bus transfer is terminated with an AHB-Lite bus error and a fault is generated (and possibly recorded in the fault report structure(s)). '0x0000'-'0xfffe': Number of clock cycles. '0xffff': This value is the default/reset value and specifies that no timeout detection is performed: a bus transfer will never be terminated and a fault will never be generated.

20.34.2 PERI_TR_CMD

Description: Trigger command

Address: 0x40000220

Offset: 0x220

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides SW control over trigger activation. This is useful for SW initiated triggers (e.g. DW/DMA transfers) or for debugging purposes. The control enables SW activation of one specific input trigger or output trigger of the trigger multiplexer structure.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TR_SEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			GROUP_SEL [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ACTIVATE [31:31]	OUT_SEL [30:30]	TR_EDGE [29:29]	None [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TR_SEL	RW	RW	0	Specifies the activated trigger when ACTIVATE is '1'. If the specified trigger is not present, the trigger activation has no effect.
8:12	GROUP_SEL	RW	RW	0	Specifies the trigger group: '0'-'15': trigger multiplexer groups. '16'-'31': trigger 1-to-1 groups.
29	TR_EDGE	RW	RW	0	Specifies if the activated trigger is treated as a level sensitive or edge sensitive trigger. '0': level sensitive. The trigger reflects TR_CMD.ACTIVATE. '1': edge sensitive trigger. The trigger is activated for two clk_peri cycles.
30	OUT_SEL	RW	RW	0	Specifies whether trigger activation is for a specific input or output trigger of the trigger multiplexer. Activation of a specific input trigger, will result in activation of all output triggers that have the specific input trigger selected through their TR_OUT_CTL.TR_SEL field. Activation of a specific output trigger, will result in activation of the specified TR_SEL output trigger only. '0': TR_SEL selection and trigger activation is for an input trigger to the trigger multiplexer. '1': TR_SEL selection and trigger activation is for an output trigger from the trigger multiplexer. Note: this field is not used for trigger 1-to-1 groups.

Bits	Name	SW	HW	Default or Enum	Description
31	ACTIVATE	RW	RW	0	SW sets this field to '1' to activate (set to '1') a trigger as identified by TR_SEL, TR_EDGE and OUT_SEL. HW sets this field to '0' for edge sensitive triggers AFTER the selected trigger is activated for two clk_peri cycles. Note: when ACTIVATE is '1', SW should not modify the other register fields. SW MUST NOT set ACTIVATE bit to '1' while updating the other register bits simultaneously. At first the SW MUST update the other register bits as needed, and then set ACTIVATE to '1' with a new register write.

20.34.3 PERI_ECC_CTL

Description: ECC control
Address: 0x40002000
Offset: 0x2000
Retention: Retained
IsDeepSleep: No
Comment: This register provides ECC support for the protection structures SRAM in the master interfaces peripheral (peripheral group 0, peripheral 1).
Default: 0x10000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WORD_ADDR [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					WORD_ADDR [10:8]		
Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					ECC_INJ_EN [18:18]	None [17:17]	ECC_EN [16:16]
Bits	31	30	29	28	27	26	25	24
Name	PARITY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:10	WORD_ADDR	RW	RW	0	Specifies the word address where the parity is injected. - On a 32-bit write access to this SRAM address and when ECC_INJ_EN bit is '1', the parity (PARITY) is injected.
16	ECC_EN	RW	RW	1	Enable ECC: '0': Disabled (on write ECC parity bits will not be correctly written). '1': Enabled.
18	ECC_INJ_EN	RW	RW	0	Enable error injection for PERI protection structure SRAM. When '1', the parity (PARITY) is used when a write is done to the WORD_ADDR word address of the SRAM.
24:31	PARITY	RW	RW	0	ECC parity to use for ECC error injection at address WORD_ADDR.

20.34.4 GR

20.34.4.1 PERI_GR_CLOCK_CTL

Description: Clock control
Address: 0x40004000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: The peripheral interconnect supports up to sixteen groups: group 0, group 1, ..., group 15. Peripheral groups 0, 1 and 2 use clk_slow (clk_group[0] = clk_group[1] = clk_group[2] = clk_slow) and do NOT have a CLOCK_GROUP_DIV_CTL register. Peripheral groups 3, 4, ..., 15 have a dedicated CLOCK_GROUP_DIV_CTL register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INT8_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:15	INT8_DIV	RW	RW	0	Specifies a group clock divider (from the peripheral clock 'clk_peri' to the group clock 'clk_group[3/4/5/...15]'). Integer division by (1+INT8_DIV). Allows for integer divisions in the range [1, 256]. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

20.34.4.2 PERI_GR_SL_CTL

Description: Slave control
Address: 0x40004010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ENABLED_7 [7:7]	ENABLED_6 [6:6]	ENABLED_5 [5:5]	ENABLED_4 [4:4]	ENABLED_3 [3:3]	ENABLED_2 [2:2]	ENABLED_1 [1:1]	ENABLED_0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	ENABLED_15 [15:15]	ENABLED_14 [14:14]	ENABLED_13 [13:13]	ENABLED_12 [12:12]	ENABLED_11 [11:11]	ENABLED_10 [10:10]	ENABLED_9 [9:9]	ENABLED_8 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLED_0	RW	RW	1	Peripheral group, slave 0 enable. If the slave is disabled, its clock is gated off (constant '0') and its resets are activated. Note: For peripheral group 0 (the peripheral interconnect MMIO registers), this field is a constant '1' (SW: R): the slave can NOT be disabled.
1	ENABLED_1	RW	RW	1	Peripheral group, slave 1 enable. If the slave is disabled, its clock is gated off (constant '0') and its resets are activated. Note: For peripheral group 0 (the peripheral interconnect, master interface MMIO registers), this field is a constant '1' (SW: R): the slave can NOT be disabled.
2	ENABLED_2	RW	RW	1	Peripheral group, slave 2 enable. If the slave is disabled, its clock is gated off (constant '0') and its resets are activated. Note: For peripheral group 0 (the peripheral interconnect, PCLK group MMIO registers), this field is a constant '1' (SW: R): the slave can NOT be disabled.
3	ENABLED_3	RW	RW	1	N/A
4	ENABLED_4	RW	RW	1	N/A
5	ENABLED_5	RW	RW	1	N/A
6	ENABLED_6	RW	RW	1	N/A
7	ENABLED_7	RW	RW	1	N/A
8	ENABLED_8	RW	RW	1	N/A
9	ENABLED_9	RW	RW	1	N/A
10	ENABLED_10	RW	RW	1	N/A
11	ENABLED_11	RW	RW	1	N/A
12	ENABLED_12	RW	RW	1	N/A

Bits	Name	SW	HW	Default or Enum	Description
13	ENABLED_13	RW	RW	1	N/A
14	ENABLED_14	RW	RW	1	N/A
15	ENABLED_15	RW	RW	1	N/A

20.34.5 TR_GR

20.34.5.1 PERI_TR_GR_TR_CTL

Description: Trigger control register

Address: 0x40008000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: This register specifies the input trigger for a specific output trigger in trigger group 0. Note that for SW initiated triggers, SW is responsible for activating the output trigger, rather than relying on a specific HW input trigger. For this reason, input trigger 0 is typically connected to a constant signal level of '0' at chip integration (design decision) and SW initiated output triggers are all connected to input trigger 0 (SW responsibility: TR_OUT_CTL.TR_SEL should be set to '0' to select the constant signal level '0' from chip level). As a result, SW initiated triggers can never be activated by a HW input trigger to the trigger multiplexer.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TR_SEL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DBG_FREEZE_EN [12:12]	None [11:10]		TR_EDGE [9:9]	TR_INV [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TR_SEL	RW	RW	0	Specifies input trigger. This field is typically set during the setup of a chip use case scenario. Changing this field while activated triggers are present on the input triggers may result in unpredictable behavior. Note that input trigger 0 (default value) is typically connected to a constant signal level of '0', and as a result will not cause HW activation of the output trigger.
8	TR_INV	RW	RW	0	Specifies if the output trigger is inverted.
9	TR_EDGE	RW	RW	0	Specifies if the (inverted) output trigger is treated as a level sensitive or edge sensitive trigger. '0': level sensitive. '1': edge sensitive trigger. The (inverted) output trigger duration needs to be at least 2 cycles on the consumer clock. the(inverted) output trigger is synchronized to the consumer clock and a two cycle pulse is generated on the consumer clock.
12	DBG_FREEZE_EN	RW	RW	0	Specifies if the output trigger is blocked in debug mode. When set high tr_dbg_freeze will block the output trigger generation.

20.34.6 TR_1TO1_GR

20.34.6.1 PERI_TR_1TO1_GR_TR_CTL

Description: Trigger control register
Address: 0x4000C000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							TR_SEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DBG_FREEZE_EN [12:12]	None [11:10]		TR_EDGE [9:9]	TR_INV [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_SEL	RW	RW	0	Specifies input trigger: '0': constant signal level '0'. '1': input trigger.
8	TR_INV	RW	RW	0	Specifies if the output trigger is inverted.
9	TR_EDGE	RW	RW	0	Specifies if the (inverted) output trigger is treated as a level sensitive or edge sensitive trigger. '0': level sensitive. '1': edge sensitive trigger. The (inverted) output trigger duration needs to be at least 2 cycles on the consumer clock. the(inverted) output trigger is synchronized to the consumer clock and a two cycle pulse is generated on the consumer clock.
12	DBG_FREEZE_EN	RW	RW	0	Specifies if the output trigger is blocked in debug mode. When set high tr_dbg_freeze will block the output trigger generation.

21 PERI_MS

Description	Peripheral interconnect, master interface
Base Address	0x40020000
Size	0x20000
Slave Num	MMIO0 - 1

21.1 PPU_PR 0

Register Name	Address	Permission	Description
PERI_MS_PPU_PR0_SL_ADDR	0x40020000	FULL	Slave region, base address
PERI_MS_PPU_PR0_SL_SIZE	0x40020004	FULL	Slave region, size
PERI_MS_PPU_PR0_SL_ATT0	0x40020010	FULL	Slave attributes 0
PERI_MS_PPU_PR0_SL_ATT1	0x40020014	FULL	Slave attributes 1
PERI_MS_PPU_PR0_SL_ATT2	0x40020018	FULL	Slave attributes 2
PERI_MS_PPU_PR0_SL_ATT3	0x4002001C	FULL	Slave attributes 3
PERI_MS_PPU_PR0_MS_ADDR	0x40020020	FULL	Master region, base address
PERI_MS_PPU_PR0_MS_SIZE	0x40020024	FULL	Master region, size
PERI_MS_PPU_PR0_MS_ATT0	0x40020030	FULL	Master attributes 0
PERI_MS_PPU_PR0_MS_ATT1	0x40020034	FULL	Master attributes 1
PERI_MS_PPU_PR0_MS_ATT2	0x40020038	FULL	Master attributes 2
PERI_MS_PPU_PR0_MS_ATT3	0x4002003C	FULL	Master attributes 3

21.2 PPU_PR 1

Register Name	Address	Permission	Description
PERI_MS_PPU_PR1_SL_ADDR	0x40020040	FULL	Slave region, base address
PERI_MS_PPU_PR1_SL_SIZE	0x40020044	FULL	Slave region, size
PERI_MS_PPU_PR1_SL_ATT0	0x40020050	FULL	Slave attributes 0
PERI_MS_PPU_PR1_SL_ATT1	0x40020054	FULL	Slave attributes 1
PERI_MS_PPU_PR1_SL_ATT2	0x40020058	FULL	Slave attributes 2
PERI_MS_PPU_PR1_SL_ATT3	0x4002005C	FULL	Slave attributes 3
PERI_MS_PPU_PR1_MS_ADDR	0x40020060	FULL	Master region, base address
PERI_MS_PPU_PR1_MS_SIZE	0x40020064	FULL	Master region, size
PERI_MS_PPU_PR1_MS_ATT0	0x40020070	FULL	Master attributes 0
PERI_MS_PPU_PR1_MS_ATT1	0x40020074	FULL	Master attributes 1
PERI_MS_PPU_PR1_MS_ATT2	0x40020078	FULL	Master attributes 2
PERI_MS_PPU_PR1_MS_ATT3	0x4002007C	FULL	Master attributes 3

21.3 PPU_PR 2

Register Name	Address	Permission	Description
PERI_MS_PPU_PR2_SL_ADDR	0x40020080	FULL	Slave region, base address
PERI_MS_PPU_PR2_SL_SIZE	0x40020084	FULL	Slave region, size
PERI_MS_PPU_PR2_SL_ATT0	0x40020090	FULL	Slave attributes 0
PERI_MS_PPU_PR2_SL_ATT1	0x40020094	FULL	Slave attributes 1
PERI_MS_PPU_PR2_SL_ATT2	0x40020098	FULL	Slave attributes 2
PERI_MS_PPU_PR2_SL_ATT3	0x4002009C	FULL	Slave attributes 3
PERI_MS_PPU_PR2_MS_ADDR	0x400200A0	FULL	Master region, base address
PERI_MS_PPU_PR2_MS_SIZE	0x400200A4	FULL	Master region, size
PERI_MS_PPU_PR2_MS_ATT0	0x400200B0	FULL	Master attributes 0
PERI_MS_PPU_PR2_MS_ATT1	0x400200B4	FULL	Master attributes 1
PERI_MS_PPU_PR2_MS_ATT2	0x400200B8	FULL	Master attributes 2
PERI_MS_PPU_PR2_MS_ATT3	0x400200BC	FULL	Master attributes 3

21.4 PPU_PR 3

Register Name	Address	Permission	Description
PERI_MS_PPU_PR3_SL_ADDR	0x400200C0	FULL	Slave region, base address
PERI_MS_PPU_PR3_SL_SIZE	0x400200C4	FULL	Slave region, size
PERI_MS_PPU_PR3_SL_ATT0	0x400200D0	FULL	Slave attributes 0
PERI_MS_PPU_PR3_SL_ATT1	0x400200D4	FULL	Slave attributes 1
PERI_MS_PPU_PR3_SL_ATT2	0x400200D8	FULL	Slave attributes 2
PERI_MS_PPU_PR3_SL_ATT3	0x400200DC	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_PR3_MS_ADDR	0x400200E0	FULL	Master region, base address
PERI_MS_PPU_PR3_MS_SIZE	0x400200E4	FULL	Master region, size
PERI_MS_PPU_PR3_MS_ATT0	0x400200F0	FULL	Master attributes 0
PERI_MS_PPU_PR3_MS_ATT1	0x400200F4	FULL	Master attributes 1
PERI_MS_PPU_PR3_MS_ATT2	0x400200F8	FULL	Master attributes 2
PERI_MS_PPU_PR3_MS_ATT3	0x400200FC	FULL	Master attributes 3

21.5 PPU_PR 4

Register Name	Address	Permission	Description
PERI_MS_PPU_PR4_SL_ADDR	0x40020100	FULL	Slave region, base address
PERI_MS_PPU_PR4_SL_SIZE	0x40020104	FULL	Slave region, size
PERI_MS_PPU_PR4_SL_ATT0	0x40020110	FULL	Slave attributes 0
PERI_MS_PPU_PR4_SL_ATT1	0x40020114	FULL	Slave attributes 1
PERI_MS_PPU_PR4_SL_ATT2	0x40020118	FULL	Slave attributes 2
PERI_MS_PPU_PR4_SL_ATT3	0x4002011C	FULL	Slave attributes 3
PERI_MS_PPU_PR4_MS_ADDR	0x40020120	FULL	Master region, base address
PERI_MS_PPU_PR4_MS_SIZE	0x40020124	FULL	Master region, size
PERI_MS_PPU_PR4_MS_ATT0	0x40020130	FULL	Master attributes 0
PERI_MS_PPU_PR4_MS_ATT1	0x40020134	FULL	Master attributes 1
PERI_MS_PPU_PR4_MS_ATT2	0x40020138	FULL	Master attributes 2
PERI_MS_PPU_PR4_MS_ATT3	0x4002013C	FULL	Master attributes 3

21.6 PPU_PR 5

Register Name	Address	Permission	Description
PERI_MS_PPU_PR5_SL_ADDR	0x40020140	FULL	Slave region, base address
PERI_MS_PPU_PR5_SL_SIZE	0x40020144	FULL	Slave region, size
PERI_MS_PPU_PR5_SL_ATT0	0x40020150	FULL	Slave attributes 0
PERI_MS_PPU_PR5_SL_ATT1	0x40020154	FULL	Slave attributes 1
PERI_MS_PPU_PR5_SL_ATT2	0x40020158	FULL	Slave attributes 2
PERI_MS_PPU_PR5_SL_ATT3	0x4002015C	FULL	Slave attributes 3
PERI_MS_PPU_PR5_MS_ADDR	0x40020160	FULL	Master region, base address
PERI_MS_PPU_PR5_MS_SIZE	0x40020164	FULL	Master region, size
PERI_MS_PPU_PR5_MS_ATT0	0x40020170	FULL	Master attributes 0
PERI_MS_PPU_PR5_MS_ATT1	0x40020174	FULL	Master attributes 1
PERI_MS_PPU_PR5_MS_ATT2	0x40020178	FULL	Master attributes 2
PERI_MS_PPU_PR5_MS_ATT3	0x4002017C	FULL	Master attributes 3

21.7 PPU_PR 6

Register Name	Address	Permission	Description
PERI_MS_PPU_PR6_SL_ADDR	0x40020180	FULL	Slave region, base address
PERI_MS_PPU_PR6_SL_SIZE	0x40020184	FULL	Slave region, size
PERI_MS_PPU_PR6_SL_ATT0	0x40020190	FULL	Slave attributes 0
PERI_MS_PPU_PR6_SL_ATT1	0x40020194	FULL	Slave attributes 1
PERI_MS_PPU_PR6_SL_ATT2	0x40020198	FULL	Slave attributes 2
PERI_MS_PPU_PR6_SL_ATT3	0x4002019C	FULL	Slave attributes 3
PERI_MS_PPU_PR6_MS_ADDR	0x400201A0	FULL	Master region, base address
PERI_MS_PPU_PR6_MS_SIZE	0x400201A4	FULL	Master region, size
PERI_MS_PPU_PR6_MS_ATT0	0x400201B0	FULL	Master attributes 0
PERI_MS_PPU_PR6_MS_ATT1	0x400201B4	FULL	Master attributes 1
PERI_MS_PPU_PR6_MS_ATT2	0x400201B8	FULL	Master attributes 2
PERI_MS_PPU_PR6_MS_ATT3	0x400201BC	FULL	Master attributes 3

21.8 PPU_PR 7

Register Name	Address	Permission	Description
PERI_MS_PPU_PR7_SL_ADDR	0x400201C0	FULL	Slave region, base address
PERI_MS_PPU_PR7_SL_SIZE	0x400201C4	FULL	Slave region, size
PERI_MS_PPU_PR7_SL_ATT0	0x400201D0	FULL	Slave attributes 0
PERI_MS_PPU_PR7_SL_ATT1	0x400201D4	FULL	Slave attributes 1
PERI_MS_PPU_PR7_SL_ATT2	0x400201D8	FULL	Slave attributes 2
PERI_MS_PPU_PR7_SL_ATT3	0x400201DC	FULL	Slave attributes 3
PERI_MS_PPU_PR7_MS_ADDR	0x400201E0	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_PR7_MS_SIZE	0x400201E4	FULL	Master region, size
PERI_MS_PPU_PR7_MS_ATT0	0x400201F0	FULL	Master attributes 0
PERI_MS_PPU_PR7_MS_ATT1	0x400201F4	FULL	Master attributes 1
PERI_MS_PPU_PR7_MS_ATT2	0x400201F8	FULL	Master attributes 2
PERI_MS_PPU_PR7_MS_ATT3	0x400201FC	FULL	Master attributes 3

21.9 PPU_PR 8

Register Name	Address	Permission	Description
PERI_MS_PPU_PR8_SL_ADDR	0x40020200	FULL	Slave region, base address
PERI_MS_PPU_PR8_SL_SIZE	0x40020204	FULL	Slave region, size
PERI_MS_PPU_PR8_SL_ATT0	0x40020210	FULL	Slave attributes 0
PERI_MS_PPU_PR8_SL_ATT1	0x40020214	FULL	Slave attributes 1
PERI_MS_PPU_PR8_SL_ATT2	0x40020218	FULL	Slave attributes 2
PERI_MS_PPU_PR8_SL_ATT3	0x4002021C	FULL	Slave attributes 3
PERI_MS_PPU_PR8_MS_ADDR	0x40020220	FULL	Master region, base address
PERI_MS_PPU_PR8_MS_SIZE	0x40020224	FULL	Master region, size
PERI_MS_PPU_PR8_MS_ATT0	0x40020230	FULL	Master attributes 0
PERI_MS_PPU_PR8_MS_ATT1	0x40020234	FULL	Master attributes 1
PERI_MS_PPU_PR8_MS_ATT2	0x40020238	FULL	Master attributes 2
PERI_MS_PPU_PR8_MS_ATT3	0x4002023C	FULL	Master attributes 3

21.10 PPU_PR 9

Register Name	Address	Permission	Description
PERI_MS_PPU_PR9_SL_ADDR	0x40020240	FULL	Slave region, base address
PERI_MS_PPU_PR9_SL_SIZE	0x40020244	FULL	Slave region, size
PERI_MS_PPU_PR9_SL_ATT0	0x40020250	FULL	Slave attributes 0
PERI_MS_PPU_PR9_SL_ATT1	0x40020254	FULL	Slave attributes 1
PERI_MS_PPU_PR9_SL_ATT2	0x40020258	FULL	Slave attributes 2
PERI_MS_PPU_PR9_SL_ATT3	0x4002025C	FULL	Slave attributes 3
PERI_MS_PPU_PR9_MS_ADDR	0x40020260	FULL	Master region, base address
PERI_MS_PPU_PR9_MS_SIZE	0x40020264	FULL	Master region, size
PERI_MS_PPU_PR9_MS_ATT0	0x40020270	FULL	Master attributes 0
PERI_MS_PPU_PR9_MS_ATT1	0x40020274	FULL	Master attributes 1
PERI_MS_PPU_PR9_MS_ATT2	0x40020278	FULL	Master attributes 2
PERI_MS_PPU_PR9_MS_ATT3	0x4002027C	FULL	Master attributes 3

21.11 PPU_PR 10

Register Name	Address	Permission	Description
PERI_MS_PPU_PR10_SL_ADDR	0x40020280	FULL	Slave region, base address
PERI_MS_PPU_PR10_SL_SIZE	0x40020284	FULL	Slave region, size
PERI_MS_PPU_PR10_SL_ATT0	0x40020290	FULL	Slave attributes 0
PERI_MS_PPU_PR10_SL_ATT1	0x40020294	FULL	Slave attributes 1
PERI_MS_PPU_PR10_SL_ATT2	0x40020298	FULL	Slave attributes 2
PERI_MS_PPU_PR10_SL_ATT3	0x4002029C	FULL	Slave attributes 3
PERI_MS_PPU_PR10_MS_ADDR	0x400202A0	FULL	Master region, base address
PERI_MS_PPU_PR10_MS_SIZE	0x400202A4	FULL	Master region, size
PERI_MS_PPU_PR10_MS_ATT0	0x400202B0	FULL	Master attributes 0
PERI_MS_PPU_PR10_MS_ATT1	0x400202B4	FULL	Master attributes 1
PERI_MS_PPU_PR10_MS_ATT2	0x400202B8	FULL	Master attributes 2
PERI_MS_PPU_PR10_MS_ATT3	0x400202BC	FULL	Master attributes 3

21.12 PPU_PR 11

Register Name	Address	Permission	Description
PERI_MS_PPU_PR11_SL_ADDR	0x400202C0	FULL	Slave region, base address
PERI_MS_PPU_PR11_SL_SIZE	0x400202C4	FULL	Slave region, size
PERI_MS_PPU_PR11_SL_ATT0	0x400202D0	FULL	Slave attributes 0
PERI_MS_PPU_PR11_SL_ATT1	0x400202D4	FULL	Slave attributes 1
PERI_MS_PPU_PR11_SL_ATT2	0x400202D8	FULL	Slave attributes 2
PERI_MS_PPU_PR11_SL_ATT3	0x400202DC	FULL	Slave attributes 3
PERI_MS_PPU_PR11_MS_ADDR	0x400202E0	FULL	Master region, base address
PERI_MS_PPU_PR11_MS_SIZE	0x400202E4	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_PR11_MS_ATT0	0x400202F0	FULL	Master attributes 0
PERI_MS_PPU_PR11_MS_ATT1	0x400202F4	FULL	Master attributes 1
PERI_MS_PPU_PR11_MS_ATT2	0x400202F8	FULL	Master attributes 2
PERI_MS_PPU_PR11_MS_ATT3	0x400202FC	FULL	Master attributes 3

21.13 PPU_PR 12

Register Name	Address	Permission	Description
PERI_MS_PPU_PR12_SL_ADDR	0x40020300	FULL	Slave region, base address
PERI_MS_PPU_PR12_SL_SIZE	0x40020304	FULL	Slave region, size
PERI_MS_PPU_PR12_SL_ATT0	0x40020310	FULL	Slave attributes 0
PERI_MS_PPU_PR12_SL_ATT1	0x40020314	FULL	Slave attributes 1
PERI_MS_PPU_PR12_SL_ATT2	0x40020318	FULL	Slave attributes 2
PERI_MS_PPU_PR12_SL_ATT3	0x4002031C	FULL	Slave attributes 3
PERI_MS_PPU_PR12_MS_ADDR	0x40020320	FULL	Master region, base address
PERI_MS_PPU_PR12_MS_SIZE	0x40020324	FULL	Master region, size
PERI_MS_PPU_PR12_MS_ATT0	0x40020330	FULL	Master attributes 0
PERI_MS_PPU_PR12_MS_ATT1	0x40020334	FULL	Master attributes 1
PERI_MS_PPU_PR12_MS_ATT2	0x40020338	FULL	Master attributes 2
PERI_MS_PPU_PR12_MS_ATT3	0x4002033C	FULL	Master attributes 3

21.14 PPU_PR 13

Register Name	Address	Permission	Description
PERI_MS_PPU_PR13_SL_ADDR	0x40020340	FULL	Slave region, base address
PERI_MS_PPU_PR13_SL_SIZE	0x40020344	FULL	Slave region, size
PERI_MS_PPU_PR13_SL_ATT0	0x40020350	FULL	Slave attributes 0
PERI_MS_PPU_PR13_SL_ATT1	0x40020354	FULL	Slave attributes 1
PERI_MS_PPU_PR13_SL_ATT2	0x40020358	FULL	Slave attributes 2
PERI_MS_PPU_PR13_SL_ATT3	0x4002035C	FULL	Slave attributes 3
PERI_MS_PPU_PR13_MS_ADDR	0x40020360	FULL	Master region, base address
PERI_MS_PPU_PR13_MS_SIZE	0x40020364	FULL	Master region, size
PERI_MS_PPU_PR13_MS_ATT0	0x40020370	FULL	Master attributes 0
PERI_MS_PPU_PR13_MS_ATT1	0x40020374	FULL	Master attributes 1
PERI_MS_PPU_PR13_MS_ATT2	0x40020378	FULL	Master attributes 2
PERI_MS_PPU_PR13_MS_ATT3	0x4002037C	FULL	Master attributes 3

21.15 PPU_PR 14

Register Name	Address	Permission	Description
PERI_MS_PPU_PR14_SL_ADDR	0x40020380	FULL	Slave region, base address
PERI_MS_PPU_PR14_SL_SIZE	0x40020384	FULL	Slave region, size
PERI_MS_PPU_PR14_SL_ATT0	0x40020390	FULL	Slave attributes 0
PERI_MS_PPU_PR14_SL_ATT1	0x40020394	FULL	Slave attributes 1
PERI_MS_PPU_PR14_SL_ATT2	0x40020398	FULL	Slave attributes 2
PERI_MS_PPU_PR14_SL_ATT3	0x4002039C	FULL	Slave attributes 3
PERI_MS_PPU_PR14_MS_ADDR	0x400203A0	FULL	Master region, base address
PERI_MS_PPU_PR14_MS_SIZE	0x400203A4	FULL	Master region, size
PERI_MS_PPU_PR14_MS_ATT0	0x400203B0	FULL	Master attributes 0
PERI_MS_PPU_PR14_MS_ATT1	0x400203B4	FULL	Master attributes 1
PERI_MS_PPU_PR14_MS_ATT2	0x400203B8	FULL	Master attributes 2
PERI_MS_PPU_PR14_MS_ATT3	0x400203BC	FULL	Master attributes 3

21.16 PPU_PR 15

Register Name	Address	Permission	Description
PERI_MS_PPU_PR15_SL_ADDR	0x400203C0	FULL	Slave region, base address
PERI_MS_PPU_PR15_SL_SIZE	0x400203C4	FULL	Slave region, size
PERI_MS_PPU_PR15_SL_ATT0	0x400203D0	FULL	Slave attributes 0
PERI_MS_PPU_PR15_SL_ATT1	0x400203D4	FULL	Slave attributes 1
PERI_MS_PPU_PR15_SL_ATT2	0x400203D8	FULL	Slave attributes 2
PERI_MS_PPU_PR15_SL_ATT3	0x400203DC	FULL	Slave attributes 3
PERI_MS_PPU_PR15_MS_ADDR	0x400203E0	FULL	Master region, base address
PERI_MS_PPU_PR15_MS_SIZE	0x400203E4	FULL	Master region, size
PERI_MS_PPU_PR15_MS_ATT0	0x400203F0	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_PR15_MS_ATT1	0x400203F4	FULL	Master attributes 1
PERI_MS_PPU_PR15_MS_ATT2	0x400203F8	FULL	Master attributes 2
PERI_MS_PPU_PR15_MS_ATT3	0x400203FC	FULL	Master attributes 3

21.17 PPU_FX 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX0_SL_ADDR	0x40020800	FULL	Slave region, base address
PERI_MS_PPU_FX0_SL_SIZE	0x40020804	FULL	Slave region, size
PERI_MS_PPU_FX0_SL_ATT0	0x40020810	FULL	Slave attributes 0
PERI_MS_PPU_FX0_SL_ATT1	0x40020814	FULL	Slave attributes 1
PERI_MS_PPU_FX0_SL_ATT2	0x40020818	FULL	Slave attributes 2
PERI_MS_PPU_FX0_SL_ATT3	0x4002081C	FULL	Slave attributes 3
PERI_MS_PPU_FX0_MS_ADDR	0x40020820	FULL	Master region, base address
PERI_MS_PPU_FX0_MS_SIZE	0x40020824	FULL	Master region, size
PERI_MS_PPU_FX0_MS_ATT0	0x40020830	FULL	Master attributes 0
PERI_MS_PPU_FX0_MS_ATT1	0x40020834	FULL	Master attributes 1
PERI_MS_PPU_FX0_MS_ATT2	0x40020838	FULL	Master attributes 2
PERI_MS_PPU_FX0_MS_ATT3	0x4002083C	FULL	Master attributes 3

21.18 PPU_FX 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX1_SL_ADDR	0x40020840	FULL	Slave region, base address
PERI_MS_PPU_FX1_SL_SIZE	0x40020844	FULL	Slave region, size
PERI_MS_PPU_FX1_SL_ATT0	0x40020850	FULL	Slave attributes 0
PERI_MS_PPU_FX1_SL_ATT1	0x40020854	FULL	Slave attributes 1
PERI_MS_PPU_FX1_SL_ATT2	0x40020858	FULL	Slave attributes 2
PERI_MS_PPU_FX1_SL_ATT3	0x4002085C	FULL	Slave attributes 3
PERI_MS_PPU_FX1_MS_ADDR	0x40020860	FULL	Master region, base address
PERI_MS_PPU_FX1_MS_SIZE	0x40020864	FULL	Master region, size
PERI_MS_PPU_FX1_MS_ATT0	0x40020870	FULL	Master attributes 0
PERI_MS_PPU_FX1_MS_ATT1	0x40020874	FULL	Master attributes 1
PERI_MS_PPU_FX1_MS_ATT2	0x40020878	FULL	Master attributes 2
PERI_MS_PPU_FX1_MS_ATT3	0x4002087C	FULL	Master attributes 3

21.19 PPU_FX 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX2_SL_ADDR	0x40020880	FULL	Slave region, base address
PERI_MS_PPU_FX2_SL_SIZE	0x40020884	FULL	Slave region, size
PERI_MS_PPU_FX2_SL_ATT0	0x40020890	FULL	Slave attributes 0
PERI_MS_PPU_FX2_SL_ATT1	0x40020894	FULL	Slave attributes 1
PERI_MS_PPU_FX2_SL_ATT2	0x40020898	FULL	Slave attributes 2
PERI_MS_PPU_FX2_SL_ATT3	0x4002089C	FULL	Slave attributes 3
PERI_MS_PPU_FX2_MS_ADDR	0x400208A0	FULL	Master region, base address
PERI_MS_PPU_FX2_MS_SIZE	0x400208A4	FULL	Master region, size
PERI_MS_PPU_FX2_MS_ATT0	0x400208B0	FULL	Master attributes 0
PERI_MS_PPU_FX2_MS_ATT1	0x400208B4	FULL	Master attributes 1
PERI_MS_PPU_FX2_MS_ATT2	0x400208B8	FULL	Master attributes 2
PERI_MS_PPU_FX2_MS_ATT3	0x400208BC	FULL	Master attributes 3

21.20 PPU_FX 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX3_SL_ADDR	0x400208C0	FULL	Slave region, base address
PERI_MS_PPU_FX3_SL_SIZE	0x400208C4	FULL	Slave region, size
PERI_MS_PPU_FX3_SL_ATT0	0x400208D0	FULL	Slave attributes 0
PERI_MS_PPU_FX3_SL_ATT1	0x400208D4	FULL	Slave attributes 1
PERI_MS_PPU_FX3_SL_ATT2	0x400208D8	FULL	Slave attributes 2
PERI_MS_PPU_FX3_SL_ATT3	0x400208DC	FULL	Slave attributes 3
PERI_MS_PPU_FX3_MS_ADDR	0x400208E0	FULL	Master region, base address
PERI_MS_PPU_FX3_MS_SIZE	0x400208E4	FULL	Master region, size
PERI_MS_PPU_FX3_MS_ATT0	0x400208F0	FULL	Master attributes 0
PERI_MS_PPU_FX3_MS_ATT1	0x400208F4	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX3_MS_ATT2	0x400208F8	FULL	Master attributes 2
PERI_MS_PPU_FX3_MS_ATT3	0x400208FC	FULL	Master attributes 3

21.21 PPU_FX 4

Register Name	Address	Permission	Description
PERI_MS_PPU_FX4_SL_ADDR	0x40020900	FULL	Slave region, base address
PERI_MS_PPU_FX4_SL_SIZE	0x40020904	FULL	Slave region, size
PERI_MS_PPU_FX4_SL_ATT0	0x40020910	FULL	Slave attributes 0
PERI_MS_PPU_FX4_SL_ATT1	0x40020914	FULL	Slave attributes 1
PERI_MS_PPU_FX4_SL_ATT2	0x40020918	FULL	Slave attributes 2
PERI_MS_PPU_FX4_SL_ATT3	0x4002091C	FULL	Slave attributes 3
PERI_MS_PPU_FX4_MS_ADDR	0x40020920	FULL	Master region, base address
PERI_MS_PPU_FX4_MS_SIZE	0x40020924	FULL	Master region, size
PERI_MS_PPU_FX4_MS_ATT0	0x40020930	FULL	Master attributes 0
PERI_MS_PPU_FX4_MS_ATT1	0x40020934	FULL	Master attributes 1
PERI_MS_PPU_FX4_MS_ATT2	0x40020938	FULL	Master attributes 2
PERI_MS_PPU_FX4_MS_ATT3	0x4002093C	FULL	Master attributes 3

21.22 PPU_FX 5

Register Name	Address	Permission	Description
PERI_MS_PPU_FX5_SL_ADDR	0x40020940	FULL	Slave region, base address
PERI_MS_PPU_FX5_SL_SIZE	0x40020944	FULL	Slave region, size
PERI_MS_PPU_FX5_SL_ATT0	0x40020950	FULL	Slave attributes 0
PERI_MS_PPU_FX5_SL_ATT1	0x40020954	FULL	Slave attributes 1
PERI_MS_PPU_FX5_SL_ATT2	0x40020958	FULL	Slave attributes 2
PERI_MS_PPU_FX5_SL_ATT3	0x4002095C	FULL	Slave attributes 3
PERI_MS_PPU_FX5_MS_ADDR	0x40020960	FULL	Master region, base address
PERI_MS_PPU_FX5_MS_SIZE	0x40020964	FULL	Master region, size
PERI_MS_PPU_FX5_MS_ATT0	0x40020970	FULL	Master attributes 0
PERI_MS_PPU_FX5_MS_ATT1	0x40020974	FULL	Master attributes 1
PERI_MS_PPU_FX5_MS_ATT2	0x40020978	FULL	Master attributes 2
PERI_MS_PPU_FX5_MS_ATT3	0x4002097C	FULL	Master attributes 3

21.23 PPU_FX 6

Register Name	Address	Permission	Description
PERI_MS_PPU_FX6_SL_ADDR	0x40020980	FULL	Slave region, base address
PERI_MS_PPU_FX6_SL_SIZE	0x40020984	FULL	Slave region, size
PERI_MS_PPU_FX6_SL_ATT0	0x40020990	FULL	Slave attributes 0
PERI_MS_PPU_FX6_SL_ATT1	0x40020994	FULL	Slave attributes 1
PERI_MS_PPU_FX6_SL_ATT2	0x40020998	FULL	Slave attributes 2
PERI_MS_PPU_FX6_SL_ATT3	0x4002099C	FULL	Slave attributes 3
PERI_MS_PPU_FX6_MS_ADDR	0x400209A0	FULL	Master region, base address
PERI_MS_PPU_FX6_MS_SIZE	0x400209A4	FULL	Master region, size
PERI_MS_PPU_FX6_MS_ATT0	0x400209B0	FULL	Master attributes 0
PERI_MS_PPU_FX6_MS_ATT1	0x400209B4	FULL	Master attributes 1
PERI_MS_PPU_FX6_MS_ATT2	0x400209B8	FULL	Master attributes 2
PERI_MS_PPU_FX6_MS_ATT3	0x400209BC	FULL	Master attributes 3

21.24 PPU_FX 7

Register Name	Address	Permission	Description
PERI_MS_PPU_FX7_SL_ADDR	0x400209C0	FULL	Slave region, base address
PERI_MS_PPU_FX7_SL_SIZE	0x400209C4	FULL	Slave region, size
PERI_MS_PPU_FX7_SL_ATT0	0x400209D0	FULL	Slave attributes 0
PERI_MS_PPU_FX7_SL_ATT1	0x400209D4	FULL	Slave attributes 1
PERI_MS_PPU_FX7_SL_ATT2	0x400209D8	FULL	Slave attributes 2
PERI_MS_PPU_FX7_SL_ATT3	0x400209DC	FULL	Slave attributes 3
PERI_MS_PPU_FX7_MS_ADDR	0x400209E0	FULL	Master region, base address
PERI_MS_PPU_FX7_MS_SIZE	0x400209E4	FULL	Master region, size
PERI_MS_PPU_FX7_MS_ATT0	0x400209F0	FULL	Master attributes 0
PERI_MS_PPU_FX7_MS_ATT1	0x400209F4	FULL	Master attributes 1
PERI_MS_PPU_FX7_MS_ATT2	0x400209F8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX7_MS_ATT3	0x400209FC	FULL	Master attributes 3

21.25 PPU_FX 8

Register Name	Address	Permission	Description
PERI_MS_PPU_FX8_SL_ADDR	0x40020A00	FULL	Slave region, base address
PERI_MS_PPU_FX8_SL_SIZE	0x40020A04	FULL	Slave region, size
PERI_MS_PPU_FX8_SL_ATT0	0x40020A10	FULL	Slave attributes 0
PERI_MS_PPU_FX8_SL_ATT1	0x40020A14	FULL	Slave attributes 1
PERI_MS_PPU_FX8_SL_ATT2	0x40020A18	FULL	Slave attributes 2
PERI_MS_PPU_FX8_SL_ATT3	0x40020A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX8_MS_ADDR	0x40020A20	FULL	Master region, base address
PERI_MS_PPU_FX8_MS_SIZE	0x40020A24	FULL	Master region, size
PERI_MS_PPU_FX8_MS_ATT0	0x40020A30	FULL	Master attributes 0
PERI_MS_PPU_FX8_MS_ATT1	0x40020A34	FULL	Master attributes 1
PERI_MS_PPU_FX8_MS_ATT2	0x40020A38	FULL	Master attributes 2
PERI_MS_PPU_FX8_MS_ATT3	0x40020A3C	FULL	Master attributes 3

21.26 PPU_FX 9

Register Name	Address	Permission	Description
PERI_MS_PPU_FX9_SL_ADDR	0x40020A40	FULL	Slave region, base address
PERI_MS_PPU_FX9_SL_SIZE	0x40020A44	FULL	Slave region, size
PERI_MS_PPU_FX9_SL_ATT0	0x40020A50	FULL	Slave attributes 0
PERI_MS_PPU_FX9_SL_ATT1	0x40020A54	FULL	Slave attributes 1
PERI_MS_PPU_FX9_SL_ATT2	0x40020A58	FULL	Slave attributes 2
PERI_MS_PPU_FX9_SL_ATT3	0x40020A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX9_MS_ADDR	0x40020A60	FULL	Master region, base address
PERI_MS_PPU_FX9_MS_SIZE	0x40020A64	FULL	Master region, size
PERI_MS_PPU_FX9_MS_ATT0	0x40020A70	FULL	Master attributes 0
PERI_MS_PPU_FX9_MS_ATT1	0x40020A74	FULL	Master attributes 1
PERI_MS_PPU_FX9_MS_ATT2	0x40020A78	FULL	Master attributes 2
PERI_MS_PPU_FX9_MS_ATT3	0x40020A7C	FULL	Master attributes 3

21.27 PPU_FX 10

Register Name	Address	Permission	Description
PERI_MS_PPU_FX10_SL_ADDR	0x40020A80	FULL	Slave region, base address
PERI_MS_PPU_FX10_SL_SIZE	0x40020A84	FULL	Slave region, size
PERI_MS_PPU_FX10_SL_ATT0	0x40020A90	FULL	Slave attributes 0
PERI_MS_PPU_FX10_SL_ATT1	0x40020A94	FULL	Slave attributes 1
PERI_MS_PPU_FX10_SL_ATT2	0x40020A98	FULL	Slave attributes 2
PERI_MS_PPU_FX10_SL_ATT3	0x40020A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX10_MS_ADDR	0x40020AA0	FULL	Master region, base address
PERI_MS_PPU_FX10_MS_SIZE	0x40020AA4	FULL	Master region, size
PERI_MS_PPU_FX10_MS_ATT0	0x40020AB0	FULL	Master attributes 0
PERI_MS_PPU_FX10_MS_ATT1	0x40020AB4	FULL	Master attributes 1
PERI_MS_PPU_FX10_MS_ATT2	0x40020AB8	FULL	Master attributes 2
PERI_MS_PPU_FX10_MS_ATT3	0x40020ABC	FULL	Master attributes 3

21.28 PPU_FX 11

Register Name	Address	Permission	Description
PERI_MS_PPU_FX11_SL_ADDR	0x40020AC0	FULL	Slave region, base address
PERI_MS_PPU_FX11_SL_SIZE	0x40020AC4	FULL	Slave region, size
PERI_MS_PPU_FX11_SL_ATT0	0x40020AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX11_SL_ATT1	0x40020AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX11_SL_ATT2	0x40020AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX11_SL_ATT3	0x40020ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX11_MS_ADDR	0x40020AE0	FULL	Master region, base address
PERI_MS_PPU_FX11_MS_SIZE	0x40020AE4	FULL	Master region, size
PERI_MS_PPU_FX11_MS_ATT0	0x40020AF0	FULL	Master attributes 0
PERI_MS_PPU_FX11_MS_ATT1	0x40020AF4	FULL	Master attributes 1
PERI_MS_PPU_FX11_MS_ATT2	0x40020AF8	FULL	Master attributes 2
PERI_MS_PPU_FX11_MS_ATT3	0x40020AFC	FULL	Master attributes 3

21.29 PPU_FX 12

Register Name	Address	Permission	Description
PERI_MS_PPU_FX12_SL_ADDR	0x40020B00	FULL	Slave region, base address
PERI_MS_PPU_FX12_SL_SIZE	0x40020B04	FULL	Slave region, size
PERI_MS_PPU_FX12_SL_ATT0	0x40020B10	FULL	Slave attributes 0
PERI_MS_PPU_FX12_SL_ATT1	0x40020B14	FULL	Slave attributes 1
PERI_MS_PPU_FX12_SL_ATT2	0x40020B18	FULL	Slave attributes 2
PERI_MS_PPU_FX12_SL_ATT3	0x40020B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX12_MS_ADDR	0x40020B20	FULL	Master region, base address
PERI_MS_PPU_FX12_MS_SIZE	0x40020B24	FULL	Master region, size
PERI_MS_PPU_FX12_MS_ATT0	0x40020B30	FULL	Master attributes 0
PERI_MS_PPU_FX12_MS_ATT1	0x40020B34	FULL	Master attributes 1
PERI_MS_PPU_FX12_MS_ATT2	0x40020B38	FULL	Master attributes 2
PERI_MS_PPU_FX12_MS_ATT3	0x40020B3C	FULL	Master attributes 3

21.30 PPU_FX 13

Register Name	Address	Permission	Description
PERI_MS_PPU_FX13_SL_ADDR	0x40020B40	READ	Slave region, base address
PERI_MS_PPU_FX13_SL_SIZE	0x40020B44	READ	Slave region, size
PERI_MS_PPU_FX13_SL_ATT0	0x40020B50	READ	Slave attributes 0
PERI_MS_PPU_FX13_SL_ATT1	0x40020B54	READ	Slave attributes 1
PERI_MS_PPU_FX13_SL_ATT2	0x40020B58	READ	Slave attributes 2
PERI_MS_PPU_FX13_SL_ATT3	0x40020B5C	READ	Slave attributes 3
PERI_MS_PPU_FX13_MS_ADDR	0x40020B60	READ	Master region, base address
PERI_MS_PPU_FX13_MS_SIZE	0x40020B64	READ	Master region, size
PERI_MS_PPU_FX13_MS_ATT0	0x40020B70	READ	Master attributes 0
PERI_MS_PPU_FX13_MS_ATT1	0x40020B74	READ	Master attributes 1
PERI_MS_PPU_FX13_MS_ATT2	0x40020B78	READ	Master attributes 2
PERI_MS_PPU_FX13_MS_ATT3	0x40020B7C	READ	Master attributes 3

21.31 PPU_FX 14

Register Name	Address	Permission	Description
PERI_MS_PPU_FX14_SL_ADDR	0x40020B80	FULL	Slave region, base address
PERI_MS_PPU_FX14_SL_SIZE	0x40020B84	FULL	Slave region, size
PERI_MS_PPU_FX14_SL_ATT0	0x40020B90	FULL	Slave attributes 0
PERI_MS_PPU_FX14_SL_ATT1	0x40020B94	FULL	Slave attributes 1
PERI_MS_PPU_FX14_SL_ATT2	0x40020B98	FULL	Slave attributes 2
PERI_MS_PPU_FX14_SL_ATT3	0x40020B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX14_MS_ADDR	0x40020BA0	FULL	Master region, base address
PERI_MS_PPU_FX14_MS_SIZE	0x40020BA4	FULL	Master region, size
PERI_MS_PPU_FX14_MS_ATT0	0x40020BB0	FULL	Master attributes 0
PERI_MS_PPU_FX14_MS_ATT1	0x40020BB4	FULL	Master attributes 1
PERI_MS_PPU_FX14_MS_ATT2	0x40020BB8	FULL	Master attributes 2
PERI_MS_PPU_FX14_MS_ATT3	0x40020BBC	FULL	Master attributes 3

21.32 PPU_FX 15

Register Name	Address	Permission	Description
PERI_MS_PPU_FX15_SL_ADDR	0x40020BC0	FULL	Slave region, base address
PERI_MS_PPU_FX15_SL_SIZE	0x40020BC4	FULL	Slave region, size
PERI_MS_PPU_FX15_SL_ATT0	0x40020BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX15_SL_ATT1	0x40020BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX15_SL_ATT2	0x40020BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX15_SL_ATT3	0x40020BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX15_MS_ADDR	0x40020BE0	FULL	Master region, base address
PERI_MS_PPU_FX15_MS_SIZE	0x40020BE4	FULL	Master region, size
PERI_MS_PPU_FX15_MS_ATT0	0x40020BF0	FULL	Master attributes 0
PERI_MS_PPU_FX15_MS_ATT1	0x40020BF4	FULL	Master attributes 1
PERI_MS_PPU_FX15_MS_ATT2	0x40020BF8	FULL	Master attributes 2
PERI_MS_PPU_FX15_MS_ATT3	0x40020BFC	FULL	Master attributes 3

21.33 PPU_FX 16

Register Name	Address	Permission	Description
PERI_MS_PPU_FX16_SL_ADDR	0x40020C00	FULL	Slave region, base address
PERI_MS_PPU_FX16_SL_SIZE	0x40020C04	FULL	Slave region, size
PERI_MS_PPU_FX16_SL_ATT0	0x40020C10	FULL	Slave attributes 0
PERI_MS_PPU_FX16_SL_ATT1	0x40020C14	FULL	Slave attributes 1
PERI_MS_PPU_FX16_SL_ATT2	0x40020C18	FULL	Slave attributes 2
PERI_MS_PPU_FX16_SL_ATT3	0x40020C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX16_MS_ADDR	0x40020C20	FULL	Master region, base address
PERI_MS_PPU_FX16_MS_SIZE	0x40020C24	FULL	Master region, size
PERI_MS_PPU_FX16_MS_ATT0	0x40020C30	FULL	Master attributes 0
PERI_MS_PPU_FX16_MS_ATT1	0x40020C34	FULL	Master attributes 1
PERI_MS_PPU_FX16_MS_ATT2	0x40020C38	FULL	Master attributes 2
PERI_MS_PPU_FX16_MS_ATT3	0x40020C3C	FULL	Master attributes 3

21.34 PPU_FX 17

Register Name	Address	Permission	Description
PERI_MS_PPU_FX17_SL_ADDR	0x40020C40	FULL	Slave region, base address
PERI_MS_PPU_FX17_SL_SIZE	0x40020C44	FULL	Slave region, size
PERI_MS_PPU_FX17_SL_ATT0	0x40020C50	FULL	Slave attributes 0
PERI_MS_PPU_FX17_SL_ATT1	0x40020C54	FULL	Slave attributes 1
PERI_MS_PPU_FX17_SL_ATT2	0x40020C58	FULL	Slave attributes 2
PERI_MS_PPU_FX17_SL_ATT3	0x40020C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX17_MS_ADDR	0x40020C60	FULL	Master region, base address
PERI_MS_PPU_FX17_MS_SIZE	0x40020C64	FULL	Master region, size
PERI_MS_PPU_FX17_MS_ATT0	0x40020C70	FULL	Master attributes 0
PERI_MS_PPU_FX17_MS_ATT1	0x40020C74	FULL	Master attributes 1
PERI_MS_PPU_FX17_MS_ATT2	0x40020C78	FULL	Master attributes 2
PERI_MS_PPU_FX17_MS_ATT3	0x40020C7C	FULL	Master attributes 3

21.35 PPU_FX 18

Register Name	Address	Permission	Description
PERI_MS_PPU_FX18_SL_ADDR	0x40020C80	FULL	Slave region, base address
PERI_MS_PPU_FX18_SL_SIZE	0x40020C84	FULL	Slave region, size
PERI_MS_PPU_FX18_SL_ATT0	0x40020C90	FULL	Slave attributes 0
PERI_MS_PPU_FX18_SL_ATT1	0x40020C94	FULL	Slave attributes 1
PERI_MS_PPU_FX18_SL_ATT2	0x40020C98	FULL	Slave attributes 2
PERI_MS_PPU_FX18_SL_ATT3	0x40020C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX18_MS_ADDR	0x40020CA0	FULL	Master region, base address
PERI_MS_PPU_FX18_MS_SIZE	0x40020CA4	FULL	Master region, size
PERI_MS_PPU_FX18_MS_ATT0	0x40020CB0	FULL	Master attributes 0
PERI_MS_PPU_FX18_MS_ATT1	0x40020CB4	FULL	Master attributes 1
PERI_MS_PPU_FX18_MS_ATT2	0x40020CB8	FULL	Master attributes 2
PERI_MS_PPU_FX18_MS_ATT3	0x40020CBC	FULL	Master attributes 3

21.36 PPU_FX 19

Register Name	Address	Permission	Description
PERI_MS_PPU_FX19_SL_ADDR	0x40020CC0	FULL	Slave region, base address
PERI_MS_PPU_FX19_SL_SIZE	0x40020CC4	FULL	Slave region, size
PERI_MS_PPU_FX19_SL_ATT0	0x40020CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX19_SL_ATT1	0x40020CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX19_SL_ATT2	0x40020CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX19_SL_ATT3	0x40020CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX19_MS_ADDR	0x40020CE0	FULL	Master region, base address
PERI_MS_PPU_FX19_MS_SIZE	0x40020CE4	FULL	Master region, size
PERI_MS_PPU_FX19_MS_ATT0	0x40020CF0	FULL	Master attributes 0
PERI_MS_PPU_FX19_MS_ATT1	0x40020CF4	FULL	Master attributes 1
PERI_MS_PPU_FX19_MS_ATT2	0x40020CF8	FULL	Master attributes 2
PERI_MS_PPU_FX19_MS_ATT3	0x40020CFC	FULL	Master attributes 3

21.37 PPU_FX 20

Register Name	Address	Permission	Description
PERI_MS_PPU_FX20_SL_ADDR	0x40020D00	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX20_SL_SIZE	0x40020D04	FULL	Slave region, size
PERI_MS_PPU_FX20_SL_ATT0	0x40020D10	FULL	Slave attributes 0
PERI_MS_PPU_FX20_SL_ATT1	0x40020D14	FULL	Slave attributes 1
PERI_MS_PPU_FX20_SL_ATT2	0x40020D18	FULL	Slave attributes 2
PERI_MS_PPU_FX20_SL_ATT3	0x40020D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX20_MS_ADDR	0x40020D20	FULL	Master region, base address
PERI_MS_PPU_FX20_MS_SIZE	0x40020D24	FULL	Master region, size
PERI_MS_PPU_FX20_MS_ATT0	0x40020D30	FULL	Master attributes 0
PERI_MS_PPU_FX20_MS_ATT1	0x40020D34	FULL	Master attributes 1
PERI_MS_PPU_FX20_MS_ATT2	0x40020D38	FULL	Master attributes 2
PERI_MS_PPU_FX20_MS_ATT3	0x40020D3C	FULL	Master attributes 3

21.38 PPU_FX 21

Register Name	Address	Permission	Description
PERI_MS_PPU_FX21_SL_ADDR	0x40020D40	FULL	Slave region, base address
PERI_MS_PPU_FX21_SL_SIZE	0x40020D44	FULL	Slave region, size
PERI_MS_PPU_FX21_SL_ATT0	0x40020D50	FULL	Slave attributes 0
PERI_MS_PPU_FX21_SL_ATT1	0x40020D54	FULL	Slave attributes 1
PERI_MS_PPU_FX21_SL_ATT2	0x40020D58	FULL	Slave attributes 2
PERI_MS_PPU_FX21_SL_ATT3	0x40020D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX21_MS_ADDR	0x40020D60	FULL	Master region, base address
PERI_MS_PPU_FX21_MS_SIZE	0x40020D64	FULL	Master region, size
PERI_MS_PPU_FX21_MS_ATT0	0x40020D70	FULL	Master attributes 0
PERI_MS_PPU_FX21_MS_ATT1	0x40020D74	FULL	Master attributes 1
PERI_MS_PPU_FX21_MS_ATT2	0x40020D78	FULL	Master attributes 2
PERI_MS_PPU_FX21_MS_ATT3	0x40020D7C	FULL	Master attributes 3

21.39 PPU_FX 22

Register Name	Address	Permission	Description
PERI_MS_PPU_FX22_SL_ADDR	0x40020D80	FULL	Slave region, base address
PERI_MS_PPU_FX22_SL_SIZE	0x40020D84	FULL	Slave region, size
PERI_MS_PPU_FX22_SL_ATT0	0x40020D90	FULL	Slave attributes 0
PERI_MS_PPU_FX22_SL_ATT1	0x40020D94	FULL	Slave attributes 1
PERI_MS_PPU_FX22_SL_ATT2	0x40020D98	FULL	Slave attributes 2
PERI_MS_PPU_FX22_SL_ATT3	0x40020D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX22_MS_ADDR	0x40020DA0	FULL	Master region, base address
PERI_MS_PPU_FX22_MS_SIZE	0x40020DA4	FULL	Master region, size
PERI_MS_PPU_FX22_MS_ATT0	0x40020DB0	FULL	Master attributes 0
PERI_MS_PPU_FX22_MS_ATT1	0x40020DB4	FULL	Master attributes 1
PERI_MS_PPU_FX22_MS_ATT2	0x40020DB8	FULL	Master attributes 2
PERI_MS_PPU_FX22_MS_ATT3	0x40020DBC	FULL	Master attributes 3

21.40 PPU_FX 23

Register Name	Address	Permission	Description
PERI_MS_PPU_FX23_SL_ADDR	0x40020DC0	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX23_SL_SIZE	0x40020DC4	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX23_SL_ATT0	0x40020DD0	PRIVILEGE - WRITE	Slave attributes 0
PERI_MS_PPU_FX23_SL_ATT1	0x40020DD4	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX23_SL_ATT2	0x40020DD8	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX23_SL_ATT3	0x40020DDC	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX23_MS_ADDR	0x40020DE0	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX23_MS_SIZE	0x40020DE4	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX23_MS_ATT0	0x40020DF0	PRIVILEGE - WRITE	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX23_MS_ATT1	0x40020DF4	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX23_MS_ATT2	0x40020DF8	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX23_MS_ATT3	0x40020DFC	PRIVILEGE - WRITE	Master attributes 3

21.41 PPU_FX 24

Register Name	Address	Permission	Description
PERI_MS_PPU_FX24_SL_ADDR	0x40020E00	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX24_SL_SIZE	0x40020E04	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX24_SL_ATT0	0x40020E10	PRIVILEGE - WRITE	Slave attributes 0
PERI_MS_PPU_FX24_SL_ATT1	0x40020E14	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX24_SL_ATT2	0x40020E18	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX24_SL_ATT3	0x40020E1C	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX24_MS_ADDR	0x40020E20	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX24_MS_SIZE	0x40020E24	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX24_MS_ATT0	0x40020E30	PRIVILEGE - WRITE	Master attributes 0
PERI_MS_PPU_FX24_MS_ATT1	0x40020E34	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX24_MS_ATT2	0x40020E38	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX24_MS_ATT3	0x40020E3C	PRIVILEGE - WRITE	Master attributes 3

21.42 PPU_FX 25

Register Name	Address	Permission	Description
PERI_MS_PPU_FX25_SL_ADDR	0x40020E40	READ	Slave region, base address
PERI_MS_PPU_FX25_SL_SIZE	0x40020E44	READ	Slave region, size
PERI_MS_PPU_FX25_SL_ATT0	0x40020E50	READ	Slave attributes 0
PERI_MS_PPU_FX25_SL_ATT1	0x40020E54	READ	Slave attributes 1
PERI_MS_PPU_FX25_SL_ATT2	0x40020E58	READ	Slave attributes 2
PERI_MS_PPU_FX25_SL_ATT3	0x40020E5C	READ	Slave attributes 3
PERI_MS_PPU_FX25_MS_ADDR	0x40020E60	READ	Master region, base address
PERI_MS_PPU_FX25_MS_SIZE	0x40020E64	READ	Master region, size
PERI_MS_PPU_FX25_MS_ATT0	0x40020E70	READ	Master attributes 0
PERI_MS_PPU_FX25_MS_ATT1	0x40020E74	READ	Master attributes 1
PERI_MS_PPU_FX25_MS_ATT2	0x40020E78	READ	Master attributes 2
PERI_MS_PPU_FX25_MS_ATT3	0x40020E7C	READ	Master attributes 3

21.43 PPU_FX 26

Register Name	Address	Permission	Description
PERI_MS_PPU_FX26_SL_ADDR	0x40020E80	FULL	Slave region, base address
PERI_MS_PPU_FX26_SL_SIZE	0x40020E84	FULL	Slave region, size
PERI_MS_PPU_FX26_SL_ATT0	0x40020E90	FULL	Slave attributes 0
PERI_MS_PPU_FX26_SL_ATT1	0x40020E94	FULL	Slave attributes 1
PERI_MS_PPU_FX26_SL_ATT2	0x40020E98	FULL	Slave attributes 2
PERI_MS_PPU_FX26_SL_ATT3	0x40020E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX26_MS_ADDR	0x40020EA0	FULL	Master region, base address
PERI_MS_PPU_FX26_MS_SIZE	0x40020EA4	FULL	Master region, size
PERI_MS_PPU_FX26_MS_ATT0	0x40020EB0	FULL	Master attributes 0
PERI_MS_PPU_FX26_MS_ATT1	0x40020EB4	FULL	Master attributes 1
PERI_MS_PPU_FX26_MS_ATT2	0x40020EB8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX26_MS_ATT3	0x40020EBC	FULL	Master attributes 3

21.44 PPU_FX 27

Register Name	Address	Permission	Description
PERI_MS_PPU_FX27_SL_ADDR	0x40020EC0	FULL	Slave region, base address
PERI_MS_PPU_FX27_SL_SIZE	0x40020EC4	FULL	Slave region, size
PERI_MS_PPU_FX27_SL_ATT0	0x40020ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX27_SL_ATT1	0x40020ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX27_SL_ATT2	0x40020ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX27_SL_ATT3	0x40020EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX27_MS_ADDR	0x40020EE0	FULL	Master region, base address
PERI_MS_PPU_FX27_MS_SIZE	0x40020EE4	FULL	Master region, size
PERI_MS_PPU_FX27_MS_ATT0	0x40020EF0	FULL	Master attributes 0
PERI_MS_PPU_FX27_MS_ATT1	0x40020EF4	FULL	Master attributes 1
PERI_MS_PPU_FX27_MS_ATT2	0x40020EF8	FULL	Master attributes 2
PERI_MS_PPU_FX27_MS_ATT3	0x40020EFC	FULL	Master attributes 3

21.45 PPU_FX 28

Register Name	Address	Permission	Description
PERI_MS_PPU_FX28_SL_ADDR	0x40020F00	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX28_SL_SIZE	0x40020F04	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX28_SL_ATT0	0x40020F10	PRIVILEGE - WRITE	Slave attributes 0
PERI_MS_PPU_FX28_SL_ATT1	0x40020F14	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX28_SL_ATT2	0x40020F18	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX28_SL_ATT3	0x40020F1C	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX28_MS_ADDR	0x40020F20	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX28_MS_SIZE	0x40020F24	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX28_MS_ATT0	0x40020F30	PRIVILEGE - WRITE	Master attributes 0
PERI_MS_PPU_FX28_MS_ATT1	0x40020F34	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX28_MS_ATT2	0x40020F38	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX28_MS_ATT3	0x40020F3C	PRIVILEGE - WRITE	Master attributes 3

21.46 PPU_FX 29

Register Name	Address	Permission	Description
PERI_MS_PPU_FX29_SL_ADDR	0x40020F40	FULL	Slave region, base address
PERI_MS_PPU_FX29_SL_SIZE	0x40020F44	FULL	Slave region, size
PERI_MS_PPU_FX29_SL_ATT0	0x40020F50	FULL	Slave attributes 0
PERI_MS_PPU_FX29_SL_ATT1	0x40020F54	FULL	Slave attributes 1
PERI_MS_PPU_FX29_SL_ATT2	0x40020F58	FULL	Slave attributes 2
PERI_MS_PPU_FX29_SL_ATT3	0x40020F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX29_MS_ADDR	0x40020F60	FULL	Master region, base address
PERI_MS_PPU_FX29_MS_SIZE	0x40020F64	FULL	Master region, size
PERI_MS_PPU_FX29_MS_ATT0	0x40020F70	FULL	Master attributes 0
PERI_MS_PPU_FX29_MS_ATT1	0x40020F74	FULL	Master attributes 1
PERI_MS_PPU_FX29_MS_ATT2	0x40020F78	FULL	Master attributes 2
PERI_MS_PPU_FX29_MS_ATT3	0x40020F7C	FULL	Master attributes 3

21.47 PPU_FX 30

Register Name	Address	Permission	Description
PERI_MS_PPU_FX30_SL_ADDR	0x40020F80	FULL	Slave region, base address
PERI_MS_PPU_FX30_SL_SIZE	0x40020F84	FULL	Slave region, size
PERI_MS_PPU_FX30_SL_ATT0	0x40020F90	FULL	Slave attributes 0
PERI_MS_PPU_FX30_SL_ATT1	0x40020F94	FULL	Slave attributes 1
PERI_MS_PPU_FX30_SL_ATT2	0x40020F98	FULL	Slave attributes 2
PERI_MS_PPU_FX30_SL_ATT3	0x40020F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX30_MS_ADDR	0x40020FA0	FULL	Master region, base address
PERI_MS_PPU_FX30_MS_SIZE	0x40020FA4	FULL	Master region, size
PERI_MS_PPU_FX30_MS_ATT0	0x40020FB0	FULL	Master attributes 0
PERI_MS_PPU_FX30_MS_ATT1	0x40020FB4	FULL	Master attributes 1
PERI_MS_PPU_FX30_MS_ATT2	0x40020FB8	FULL	Master attributes 2
PERI_MS_PPU_FX30_MS_ATT3	0x40020FBC	FULL	Master attributes 3

21.48 PPU_FX 31

Register Name	Address	Permission	Description
PERI_MS_PPU_FX31_SL_ADDR	0x40020FC0	FULL	Slave region, base address
PERI_MS_PPU_FX31_SL_SIZE	0x40020FC4	FULL	Slave region, size
PERI_MS_PPU_FX31_SL_ATT0	0x40020FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX31_SL_ATT1	0x40020FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX31_SL_ATT2	0x40020FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX31_SL_ATT3	0x40020FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX31_MS_ADDR	0x40020FE0	FULL	Master region, base address
PERI_MS_PPU_FX31_MS_SIZE	0x40020FE4	FULL	Master region, size
PERI_MS_PPU_FX31_MS_ATT0	0x40020FF0	FULL	Master attributes 0
PERI_MS_PPU_FX31_MS_ATT1	0x40020FF4	FULL	Master attributes 1
PERI_MS_PPU_FX31_MS_ATT2	0x40020FF8	FULL	Master attributes 2
PERI_MS_PPU_FX31_MS_ATT3	0x40020FFC	FULL	Master attributes 3

21.49 PPU_FX 32

Register Name	Address	Permission	Description
PERI_MS_PPU_FX32_SL_ADDR	0x40021000	READ	Slave region, base address
PERI_MS_PPU_FX32_SL_SIZE	0x40021004	READ	Slave region, size
PERI_MS_PPU_FX32_SL_ATT0	0x40021010	READ	Slave attributes 0
PERI_MS_PPU_FX32_SL_ATT1	0x40021014	READ	Slave attributes 1
PERI_MS_PPU_FX32_SL_ATT2	0x40021018	READ	Slave attributes 2
PERI_MS_PPU_FX32_SL_ATT3	0x4002101C	READ	Slave attributes 3
PERI_MS_PPU_FX32_MS_ADDR	0x40021020	READ	Master region, base address
PERI_MS_PPU_FX32_MS_SIZE	0x40021024	READ	Master region, size
PERI_MS_PPU_FX32_MS_ATT0	0x40021030	READ	Master attributes 0
PERI_MS_PPU_FX32_MS_ATT1	0x40021034	READ	Master attributes 1
PERI_MS_PPU_FX32_MS_ATT2	0x40021038	READ	Master attributes 2
PERI_MS_PPU_FX32_MS_ATT3	0x4002103C	READ	Master attributes 3

21.50 PPU_FX 33

Register Name	Address	Permission	Description
PERI_MS_PPU_FX33_SL_ADDR	0x40021040	FULL	Slave region, base address
PERI_MS_PPU_FX33_SL_SIZE	0x40021044	FULL	Slave region, size
PERI_MS_PPU_FX33_SL_ATT0	0x40021050	FULL	Slave attributes 0
PERI_MS_PPU_FX33_SL_ATT1	0x40021054	FULL	Slave attributes 1
PERI_MS_PPU_FX33_SL_ATT2	0x40021058	FULL	Slave attributes 2
PERI_MS_PPU_FX33_SL_ATT3	0x4002105C	FULL	Slave attributes 3
PERI_MS_PPU_FX33_MS_ADDR	0x40021060	FULL	Master region, base address
PERI_MS_PPU_FX33_MS_SIZE	0x40021064	FULL	Master region, size
PERI_MS_PPU_FX33_MS_ATT0	0x40021070	FULL	Master attributes 0
PERI_MS_PPU_FX33_MS_ATT1	0x40021074	FULL	Master attributes 1
PERI_MS_PPU_FX33_MS_ATT2	0x40021078	FULL	Master attributes 2
PERI_MS_PPU_FX33_MS_ATT3	0x4002107C	FULL	Master attributes 3

21.51 PPU_FX 34

Register Name	Address	Permission	Description
PERI_MS_PPU_FX34_SL_ADDR	0x40021080	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX34_SL_SIZE	0x40021084	FULL	Slave region, size
PERI_MS_PPU_FX34_SL_ATT0	0x40021090	FULL	Slave attributes 0
PERI_MS_PPU_FX34_SL_ATT1	0x40021094	FULL	Slave attributes 1
PERI_MS_PPU_FX34_SL_ATT2	0x40021098	FULL	Slave attributes 2
PERI_MS_PPU_FX34_SL_ATT3	0x4002109C	FULL	Slave attributes 3
PERI_MS_PPU_FX34_MS_ADDR	0x400210A0	FULL	Master region, base address
PERI_MS_PPU_FX34_MS_SIZE	0x400210A4	FULL	Master region, size
PERI_MS_PPU_FX34_MS_ATT0	0x400210B0	FULL	Master attributes 0
PERI_MS_PPU_FX34_MS_ATT1	0x400210B4	FULL	Master attributes 1
PERI_MS_PPU_FX34_MS_ATT2	0x400210B8	FULL	Master attributes 2
PERI_MS_PPU_FX34_MS_ATT3	0x400210BC	FULL	Master attributes 3

21.52 PPU_FX 35

Register Name	Address	Permission	Description
PERI_MS_PPU_FX35_SL_ADDR	0x400210C0	FULL	Slave region, base address
PERI_MS_PPU_FX35_SL_SIZE	0x400210C4	FULL	Slave region, size
PERI_MS_PPU_FX35_SL_ATT0	0x400210D0	FULL	Slave attributes 0
PERI_MS_PPU_FX35_SL_ATT1	0x400210D4	FULL	Slave attributes 1
PERI_MS_PPU_FX35_SL_ATT2	0x400210D8	FULL	Slave attributes 2
PERI_MS_PPU_FX35_SL_ATT3	0x400210DC	FULL	Slave attributes 3
PERI_MS_PPU_FX35_MS_ADDR	0x400210E0	FULL	Master region, base address
PERI_MS_PPU_FX35_MS_SIZE	0x400210E4	FULL	Master region, size
PERI_MS_PPU_FX35_MS_ATT0	0x400210F0	FULL	Master attributes 0
PERI_MS_PPU_FX35_MS_ATT1	0x400210F4	FULL	Master attributes 1
PERI_MS_PPU_FX35_MS_ATT2	0x400210F8	FULL	Master attributes 2
PERI_MS_PPU_FX35_MS_ATT3	0x400210FC	FULL	Master attributes 3

21.53 PPU_FX 36

Register Name	Address	Permission	Description
PERI_MS_PPU_FX36_SL_ADDR	0x40021100	FULL	Slave region, base address
PERI_MS_PPU_FX36_SL_SIZE	0x40021104	FULL	Slave region, size
PERI_MS_PPU_FX36_SL_ATT0	0x40021110	FULL	Slave attributes 0
PERI_MS_PPU_FX36_SL_ATT1	0x40021114	FULL	Slave attributes 1
PERI_MS_PPU_FX36_SL_ATT2	0x40021118	FULL	Slave attributes 2
PERI_MS_PPU_FX36_SL_ATT3	0x4002111C	FULL	Slave attributes 3
PERI_MS_PPU_FX36_MS_ADDR	0x40021120	FULL	Master region, base address
PERI_MS_PPU_FX36_MS_SIZE	0x40021124	FULL	Master region, size
PERI_MS_PPU_FX36_MS_ATT0	0x40021130	FULL	Master attributes 0
PERI_MS_PPU_FX36_MS_ATT1	0x40021134	FULL	Master attributes 1
PERI_MS_PPU_FX36_MS_ATT2	0x40021138	FULL	Master attributes 2
PERI_MS_PPU_FX36_MS_ATT3	0x4002113C	FULL	Master attributes 3

21.54 PPU_FX 37

Register Name	Address	Permission	Description
PERI_MS_PPU_FX37_SL_ADDR	0x40021140	FULL	Slave region, base address
PERI_MS_PPU_FX37_SL_SIZE	0x40021144	FULL	Slave region, size
PERI_MS_PPU_FX37_SL_ATT0	0x40021150	FULL	Slave attributes 0
PERI_MS_PPU_FX37_SL_ATT1	0x40021154	FULL	Slave attributes 1
PERI_MS_PPU_FX37_SL_ATT2	0x40021158	FULL	Slave attributes 2
PERI_MS_PPU_FX37_SL_ATT3	0x4002115C	FULL	Slave attributes 3
PERI_MS_PPU_FX37_MS_ADDR	0x40021160	FULL	Master region, base address
PERI_MS_PPU_FX37_MS_SIZE	0x40021164	FULL	Master region, size
PERI_MS_PPU_FX37_MS_ATT0	0x40021170	FULL	Master attributes 0
PERI_MS_PPU_FX37_MS_ATT1	0x40021174	FULL	Master attributes 1
PERI_MS_PPU_FX37_MS_ATT2	0x40021178	FULL	Master attributes 2
PERI_MS_PPU_FX37_MS_ATT3	0x4002117C	FULL	Master attributes 3

21.55 PPU_FX 38

Register Name	Address	Permission	Description
PERI_MS_PPU_FX38_SL_ADDR	0x40021180	FULL	Slave region, base address
PERI_MS_PPU_FX38_SL_SIZE	0x40021184	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX38_SL_ATT0	0x40021190	FULL	Slave attributes 0
PERI_MS_PPU_FX38_SL_ATT1	0x40021194	FULL	Slave attributes 1
PERI_MS_PPU_FX38_SL_ATT2	0x40021198	FULL	Slave attributes 2
PERI_MS_PPU_FX38_SL_ATT3	0x4002119C	FULL	Slave attributes 3
PERI_MS_PPU_FX38_MS_ADDR	0x400211A0	FULL	Master region, base address
PERI_MS_PPU_FX38_MS_SIZE	0x400211A4	FULL	Master region, size
PERI_MS_PPU_FX38_MS_ATT0	0x400211B0	FULL	Master attributes 0
PERI_MS_PPU_FX38_MS_ATT1	0x400211B4	FULL	Master attributes 1
PERI_MS_PPU_FX38_MS_ATT2	0x400211B8	FULL	Master attributes 2
PERI_MS_PPU_FX38_MS_ATT3	0x400211BC	FULL	Master attributes 3

21.56 PPU_FX 39

Register Name	Address	Permission	Description
PERI_MS_PPU_FX39_SL_ADDR	0x400211C0	FULL	Slave region, base address
PERI_MS_PPU_FX39_SL_SIZE	0x400211C4	FULL	Slave region, size
PERI_MS_PPU_FX39_SL_ATT0	0x400211D0	FULL	Slave attributes 0
PERI_MS_PPU_FX39_SL_ATT1	0x400211D4	FULL	Slave attributes 1
PERI_MS_PPU_FX39_SL_ATT2	0x400211D8	FULL	Slave attributes 2
PERI_MS_PPU_FX39_SL_ATT3	0x400211DC	FULL	Slave attributes 3
PERI_MS_PPU_FX39_MS_ADDR	0x400211E0	FULL	Master region, base address
PERI_MS_PPU_FX39_MS_SIZE	0x400211E4	FULL	Master region, size
PERI_MS_PPU_FX39_MS_ATT0	0x400211F0	FULL	Master attributes 0
PERI_MS_PPU_FX39_MS_ATT1	0x400211F4	FULL	Master attributes 1
PERI_MS_PPU_FX39_MS_ATT2	0x400211F8	FULL	Master attributes 2
PERI_MS_PPU_FX39_MS_ATT3	0x400211FC	FULL	Master attributes 3

21.57 PPU_FX 40

Register Name	Address	Permission	Description
PERI_MS_PPU_FX40_SL_ADDR	0x40021200	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX40_SL_SIZE	0x40021204	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX40_SL_ATT0	0x40021210	PRIVILEGE - WRITE	Slave attributes 0
PERI_MS_PPU_FX40_SL_ATT1	0x40021214	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX40_SL_ATT2	0x40021218	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX40_SL_ATT3	0x4002121C	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX40_MS_ADDR	0x40021220	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX40_MS_SIZE	0x40021224	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX40_MS_ATT0	0x40021230	PRIVILEGE - WRITE	Master attributes 0
PERI_MS_PPU_FX40_MS_ATT1	0x40021234	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX40_MS_ATT2	0x40021238	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX40_MS_ATT3	0x4002123C	PRIVILEGE - WRITE	Master attributes 3

21.58 PPU_FX 41

Register Name	Address	Permission	Description
PERI_MS_PPU_FX41_SL_ADDR	0x40021240	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX41_SL_SIZE	0x40021244	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX41_SL_ATT0	0x40021250	PRIVILEGE - WRITE	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX41_SL_ATT1	0x40021254	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX41_SL_ATT2	0x40021258	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX41_SL_ATT3	0x4002125C	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX41_MS_ADDR	0x40021260	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX41_MS_SIZE	0x40021264	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX41_MS_ATT0	0x40021270	PRIVILEGE - WRITE	Master attributes 0
PERI_MS_PPU_FX41_MS_ATT1	0x40021274	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX41_MS_ATT2	0x40021278	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX41_MS_ATT3	0x4002127C	PRIVILEGE - WRITE	Master attributes 3

21.59 PPU_FX 42

Register Name	Address	Permission	Description
PERI_MS_PPU_FX42_SL_ADDR	0x40021280	PRIVILEGE - WRITE	Slave region, base address
PERI_MS_PPU_FX42_SL_SIZE	0x40021284	PRIVILEGE - WRITE	Slave region, size
PERI_MS_PPU_FX42_SL_ATT0	0x40021290	PRIVILEGE - WRITE	Slave attributes 0
PERI_MS_PPU_FX42_SL_ATT1	0x40021294	PRIVILEGE - WRITE	Slave attributes 1
PERI_MS_PPU_FX42_SL_ATT2	0x40021298	PRIVILEGE - WRITE	Slave attributes 2
PERI_MS_PPU_FX42_SL_ATT3	0x4002129C	PRIVILEGE - WRITE	Slave attributes 3
PERI_MS_PPU_FX42_MS_ADDR	0x400212A0	PRIVILEGE - WRITE	Master region, base address
PERI_MS_PPU_FX42_MS_SIZE	0x400212A4	PRIVILEGE - WRITE	Master region, size
PERI_MS_PPU_FX42_MS_ATT0	0x400212B0	PRIVILEGE - WRITE	Master attributes 0
PERI_MS_PPU_FX42_MS_ATT1	0x400212B4	PRIVILEGE - WRITE	Master attributes 1
PERI_MS_PPU_FX42_MS_ATT2	0x400212B8	PRIVILEGE - WRITE	Master attributes 2
PERI_MS_PPU_FX42_MS_ATT3	0x400212BC	PRIVILEGE - WRITE	Master attributes 3

21.60 PPU_FX 43

Register Name	Address	Permission	Description
PERI_MS_PPU_FX43_SL_ADDR	0x400212C0	FULL	Slave region, base address
PERI_MS_PPU_FX43_SL_SIZE	0x400212C4	FULL	Slave region, size
PERI_MS_PPU_FX43_SL_ATT0	0x400212D0	FULL	Slave attributes 0
PERI_MS_PPU_FX43_SL_ATT1	0x400212D4	FULL	Slave attributes 1
PERI_MS_PPU_FX43_SL_ATT2	0x400212D8	FULL	Slave attributes 2
PERI_MS_PPU_FX43_SL_ATT3	0x400212DC	FULL	Slave attributes 3
PERI_MS_PPU_FX43_MS_ADDR	0x400212E0	FULL	Master region, base address
PERI_MS_PPU_FX43_MS_SIZE	0x400212E4	FULL	Master region, size
PERI_MS_PPU_FX43_MS_ATT0	0x400212F0	FULL	Master attributes 0
PERI_MS_PPU_FX43_MS_ATT1	0x400212F4	FULL	Master attributes 1
PERI_MS_PPU_FX43_MS_ATT2	0x400212F8	FULL	Master attributes 2
PERI_MS_PPU_FX43_MS_ATT3	0x400212FC	FULL	Master attributes 3

21.61 PPU_FX 44

Register Name	Address	Permission	Description
PERI_MS_PPU_FX44_SL_ADDR	0x40021300	FULL	Slave region, base address
PERI_MS_PPU_FX44_SL_SIZE	0x40021304	FULL	Slave region, size
PERI_MS_PPU_FX44_SL_ATT0	0x40021310	FULL	Slave attributes 0
PERI_MS_PPU_FX44_SL_ATT1	0x40021314	FULL	Slave attributes 1
PERI_MS_PPU_FX44_SL_ATT2	0x40021318	FULL	Slave attributes 2
PERI_MS_PPU_FX44_SL_ATT3	0x4002131C	FULL	Slave attributes 3
PERI_MS_PPU_FX44_MS_ADDR	0x40021320	FULL	Master region, base address
PERI_MS_PPU_FX44_MS_SIZE	0x40021324	FULL	Master region, size
PERI_MS_PPU_FX44_MS_ATT0	0x40021330	FULL	Master attributes 0
PERI_MS_PPU_FX44_MS_ATT1	0x40021334	FULL	Master attributes 1
PERI_MS_PPU_FX44_MS_ATT2	0x40021338	FULL	Master attributes 2
PERI_MS_PPU_FX44_MS_ATT3	0x4002133C	FULL	Master attributes 3

21.62 PPU_FX 45

Register Name	Address	Permission	Description
PERI_MS_PPU_FX45_SL_ADDR	0x40021340	FULL	Slave region, base address
PERI_MS_PPU_FX45_SL_SIZE	0x40021344	FULL	Slave region, size
PERI_MS_PPU_FX45_SL_ATT0	0x40021350	FULL	Slave attributes 0
PERI_MS_PPU_FX45_SL_ATT1	0x40021354	FULL	Slave attributes 1
PERI_MS_PPU_FX45_SL_ATT2	0x40021358	FULL	Slave attributes 2
PERI_MS_PPU_FX45_SL_ATT3	0x4002135C	FULL	Slave attributes 3
PERI_MS_PPU_FX45_MS_ADDR	0x40021360	FULL	Master region, base address
PERI_MS_PPU_FX45_MS_SIZE	0x40021364	FULL	Master region, size
PERI_MS_PPU_FX45_MS_ATT0	0x40021370	FULL	Master attributes 0
PERI_MS_PPU_FX45_MS_ATT1	0x40021374	FULL	Master attributes 1
PERI_MS_PPU_FX45_MS_ATT2	0x40021378	FULL	Master attributes 2
PERI_MS_PPU_FX45_MS_ATT3	0x4002137C	FULL	Master attributes 3

21.63 PPU_FX 46

Register Name	Address	Permission	Description
PERI_MS_PPU_FX46_SL_ADDR	0x40021380	FULL	Slave region, base address
PERI_MS_PPU_FX46_SL_SIZE	0x40021384	FULL	Slave region, size
PERI_MS_PPU_FX46_SL_ATT0	0x40021390	FULL	Slave attributes 0
PERI_MS_PPU_FX46_SL_ATT1	0x40021394	FULL	Slave attributes 1
PERI_MS_PPU_FX46_SL_ATT2	0x40021398	FULL	Slave attributes 2
PERI_MS_PPU_FX46_SL_ATT3	0x4002139C	FULL	Slave attributes 3
PERI_MS_PPU_FX46_MS_ADDR	0x400213A0	FULL	Master region, base address
PERI_MS_PPU_FX46_MS_SIZE	0x400213A4	FULL	Master region, size
PERI_MS_PPU_FX46_MS_ATT0	0x400213B0	FULL	Master attributes 0
PERI_MS_PPU_FX46_MS_ATT1	0x400213B4	FULL	Master attributes 1
PERI_MS_PPU_FX46_MS_ATT2	0x400213B8	FULL	Master attributes 2
PERI_MS_PPU_FX46_MS_ATT3	0x400213BC	FULL	Master attributes 3

21.64 PPU_FX 47

Register Name	Address	Permission	Description
PERI_MS_PPU_FX47_SL_ADDR	0x400213C0	FULL	Slave region, base address
PERI_MS_PPU_FX47_SL_SIZE	0x400213C4	FULL	Slave region, size
PERI_MS_PPU_FX47_SL_ATT0	0x400213D0	FULL	Slave attributes 0
PERI_MS_PPU_FX47_SL_ATT1	0x400213D4	FULL	Slave attributes 1
PERI_MS_PPU_FX47_SL_ATT2	0x400213D8	FULL	Slave attributes 2
PERI_MS_PPU_FX47_SL_ATT3	0x400213DC	FULL	Slave attributes 3
PERI_MS_PPU_FX47_MS_ADDR	0x400213E0	FULL	Master region, base address
PERI_MS_PPU_FX47_MS_SIZE	0x400213E4	FULL	Master region, size
PERI_MS_PPU_FX47_MS_ATT0	0x400213F0	FULL	Master attributes 0
PERI_MS_PPU_FX47_MS_ATT1	0x400213F4	FULL	Master attributes 1
PERI_MS_PPU_FX47_MS_ATT2	0x400213F8	FULL	Master attributes 2
PERI_MS_PPU_FX47_MS_ATT3	0x400213FC	FULL	Master attributes 3

21.65 PPU_FX 48

Register Name	Address	Permission	Description
PERI_MS_PPU_FX48_SL_ADDR	0x40021400	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX48_SL_SIZE	0x40021404	FULL	Slave region, size
PERI_MS_PPU_FX48_SL_ATT0	0x40021410	FULL	Slave attributes 0
PERI_MS_PPU_FX48_SL_ATT1	0x40021414	FULL	Slave attributes 1
PERI_MS_PPU_FX48_SL_ATT2	0x40021418	FULL	Slave attributes 2
PERI_MS_PPU_FX48_SL_ATT3	0x4002141C	FULL	Slave attributes 3
PERI_MS_PPU_FX48_MS_ADDR	0x40021420	FULL	Master region, base address
PERI_MS_PPU_FX48_MS_SIZE	0x40021424	FULL	Master region, size
PERI_MS_PPU_FX48_MS_ATT0	0x40021430	FULL	Master attributes 0
PERI_MS_PPU_FX48_MS_ATT1	0x40021434	FULL	Master attributes 1
PERI_MS_PPU_FX48_MS_ATT2	0x40021438	FULL	Master attributes 2
PERI_MS_PPU_FX48_MS_ATT3	0x4002143C	FULL	Master attributes 3

21.66 PPU_FX 49

Register Name	Address	Permission	Description
PERI_MS_PPU_FX49_SL_ADDR	0x40021440	FULL	Slave region, base address
PERI_MS_PPU_FX49_SL_SIZE	0x40021444	FULL	Slave region, size
PERI_MS_PPU_FX49_SL_ATT0	0x40021450	FULL	Slave attributes 0
PERI_MS_PPU_FX49_SL_ATT1	0x40021454	FULL	Slave attributes 1
PERI_MS_PPU_FX49_SL_ATT2	0x40021458	FULL	Slave attributes 2
PERI_MS_PPU_FX49_SL_ATT3	0x4002145C	FULL	Slave attributes 3
PERI_MS_PPU_FX49_MS_ADDR	0x40021460	FULL	Master region, base address
PERI_MS_PPU_FX49_MS_SIZE	0x40021464	FULL	Master region, size
PERI_MS_PPU_FX49_MS_ATT0	0x40021470	FULL	Master attributes 0
PERI_MS_PPU_FX49_MS_ATT1	0x40021474	FULL	Master attributes 1
PERI_MS_PPU_FX49_MS_ATT2	0x40021478	FULL	Master attributes 2
PERI_MS_PPU_FX49_MS_ATT3	0x4002147C	FULL	Master attributes 3

21.67 PPU_FX 50

Register Name	Address	Permission	Description
PERI_MS_PPU_FX50_SL_ADDR	0x40021480	FULL	Slave region, base address
PERI_MS_PPU_FX50_SL_SIZE	0x40021484	FULL	Slave region, size
PERI_MS_PPU_FX50_SL_ATT0	0x40021490	FULL	Slave attributes 0
PERI_MS_PPU_FX50_SL_ATT1	0x40021494	FULL	Slave attributes 1
PERI_MS_PPU_FX50_SL_ATT2	0x40021498	FULL	Slave attributes 2
PERI_MS_PPU_FX50_SL_ATT3	0x4002149C	FULL	Slave attributes 3
PERI_MS_PPU_FX50_MS_ADDR	0x400214A0	FULL	Master region, base address
PERI_MS_PPU_FX50_MS_SIZE	0x400214A4	FULL	Master region, size
PERI_MS_PPU_FX50_MS_ATT0	0x400214B0	FULL	Master attributes 0
PERI_MS_PPU_FX50_MS_ATT1	0x400214B4	FULL	Master attributes 1
PERI_MS_PPU_FX50_MS_ATT2	0x400214B8	FULL	Master attributes 2
PERI_MS_PPU_FX50_MS_ATT3	0x400214BC	FULL	Master attributes 3

21.68 PPU_FX 51

Register Name	Address	Permission	Description
PERI_MS_PPU_FX51_SL_ADDR	0x400214C0	FULL	Slave region, base address
PERI_MS_PPU_FX51_SL_SIZE	0x400214C4	FULL	Slave region, size
PERI_MS_PPU_FX51_SL_ATT0	0x400214D0	FULL	Slave attributes 0
PERI_MS_PPU_FX51_SL_ATT1	0x400214D4	FULL	Slave attributes 1
PERI_MS_PPU_FX51_SL_ATT2	0x400214D8	FULL	Slave attributes 2
PERI_MS_PPU_FX51_SL_ATT3	0x400214DC	FULL	Slave attributes 3
PERI_MS_PPU_FX51_MS_ADDR	0x400214E0	FULL	Master region, base address
PERI_MS_PPU_FX51_MS_SIZE	0x400214E4	FULL	Master region, size
PERI_MS_PPU_FX51_MS_ATT0	0x400214F0	FULL	Master attributes 0
PERI_MS_PPU_FX51_MS_ATT1	0x400214F4	FULL	Master attributes 1
PERI_MS_PPU_FX51_MS_ATT2	0x400214F8	FULL	Master attributes 2
PERI_MS_PPU_FX51_MS_ATT3	0x400214FC	FULL	Master attributes 3

21.69 PPU_FX 52

Register Name	Address	Permission	Description
PERI_MS_PPU_FX52_SL_ADDR	0x40021500	FULL	Slave region, base address
PERI_MS_PPU_FX52_SL_SIZE	0x40021504	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX52_SL_ATT0	0x40021510	FULL	Slave attributes 0
PERI_MS_PPU_FX52_SL_ATT1	0x40021514	FULL	Slave attributes 1
PERI_MS_PPU_FX52_SL_ATT2	0x40021518	FULL	Slave attributes 2
PERI_MS_PPU_FX52_SL_ATT3	0x4002151C	FULL	Slave attributes 3
PERI_MS_PPU_FX52_MS_ADDR	0x40021520	FULL	Master region, base address
PERI_MS_PPU_FX52_MS_SIZE	0x40021524	FULL	Master region, size
PERI_MS_PPU_FX52_MS_ATT0	0x40021530	FULL	Master attributes 0
PERI_MS_PPU_FX52_MS_ATT1	0x40021534	FULL	Master attributes 1
PERI_MS_PPU_FX52_MS_ATT2	0x40021538	FULL	Master attributes 2
PERI_MS_PPU_FX52_MS_ATT3	0x4002153C	FULL	Master attributes 3

21.70 PPU_FX 53

Register Name	Address	Permission	Description
PERI_MS_PPU_FX53_SL_ADDR	0x40021540	FULL	Slave region, base address
PERI_MS_PPU_FX53_SL_SIZE	0x40021544	FULL	Slave region, size
PERI_MS_PPU_FX53_SL_ATT0	0x40021550	FULL	Slave attributes 0
PERI_MS_PPU_FX53_SL_ATT1	0x40021554	FULL	Slave attributes 1
PERI_MS_PPU_FX53_SL_ATT2	0x40021558	FULL	Slave attributes 2
PERI_MS_PPU_FX53_SL_ATT3	0x4002155C	FULL	Slave attributes 3
PERI_MS_PPU_FX53_MS_ADDR	0x40021560	FULL	Master region, base address
PERI_MS_PPU_FX53_MS_SIZE	0x40021564	FULL	Master region, size
PERI_MS_PPU_FX53_MS_ATT0	0x40021570	FULL	Master attributes 0
PERI_MS_PPU_FX53_MS_ATT1	0x40021574	FULL	Master attributes 1
PERI_MS_PPU_FX53_MS_ATT2	0x40021578	FULL	Master attributes 2
PERI_MS_PPU_FX53_MS_ATT3	0x4002157C	FULL	Master attributes 3

21.71 PPU_FX 54

Register Name	Address	Permission	Description
PERI_MS_PPU_FX54_SL_ADDR	0x40021580	FULL	Slave region, base address
PERI_MS_PPU_FX54_SL_SIZE	0x40021584	FULL	Slave region, size
PERI_MS_PPU_FX54_SL_ATT0	0x40021590	FULL	Slave attributes 0
PERI_MS_PPU_FX54_SL_ATT1	0x40021594	FULL	Slave attributes 1
PERI_MS_PPU_FX54_SL_ATT2	0x40021598	FULL	Slave attributes 2
PERI_MS_PPU_FX54_SL_ATT3	0x4002159C	FULL	Slave attributes 3
PERI_MS_PPU_FX54_MS_ADDR	0x400215A0	FULL	Master region, base address
PERI_MS_PPU_FX54_MS_SIZE	0x400215A4	FULL	Master region, size
PERI_MS_PPU_FX54_MS_ATT0	0x400215B0	FULL	Master attributes 0
PERI_MS_PPU_FX54_MS_ATT1	0x400215B4	FULL	Master attributes 1
PERI_MS_PPU_FX54_MS_ATT2	0x400215B8	FULL	Master attributes 2
PERI_MS_PPU_FX54_MS_ATT3	0x400215BC	FULL	Master attributes 3

21.72 PPU_FX 55

Register Name	Address	Permission	Description
PERI_MS_PPU_FX55_SL_ADDR	0x400215C0	FULL	Slave region, base address
PERI_MS_PPU_FX55_SL_SIZE	0x400215C4	FULL	Slave region, size
PERI_MS_PPU_FX55_SL_ATT0	0x400215D0	FULL	Slave attributes 0
PERI_MS_PPU_FX55_SL_ATT1	0x400215D4	FULL	Slave attributes 1
PERI_MS_PPU_FX55_SL_ATT2	0x400215D8	FULL	Slave attributes 2
PERI_MS_PPU_FX55_SL_ATT3	0x400215DC	FULL	Slave attributes 3
PERI_MS_PPU_FX55_MS_ADDR	0x400215E0	FULL	Master region, base address
PERI_MS_PPU_FX55_MS_SIZE	0x400215E4	FULL	Master region, size
PERI_MS_PPU_FX55_MS_ATT0	0x400215F0	FULL	Master attributes 0
PERI_MS_PPU_FX55_MS_ATT1	0x400215F4	FULL	Master attributes 1
PERI_MS_PPU_FX55_MS_ATT2	0x400215F8	FULL	Master attributes 2
PERI_MS_PPU_FX55_MS_ATT3	0x400215FC	FULL	Master attributes 3

21.73 PPU_FX 56

Register Name	Address	Permission	Description
PERI_MS_PPU_FX56_SL_ADDR	0x40021600	FULL	Slave region, base address
PERI_MS_PPU_FX56_SL_SIZE	0x40021604	FULL	Slave region, size
PERI_MS_PPU_FX56_SL_ATT0	0x40021610	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX56_SL_ATT1	0x40021614	FULL	Slave attributes 1
PERI_MS_PPU_FX56_SL_ATT2	0x40021618	FULL	Slave attributes 2
PERI_MS_PPU_FX56_SL_ATT3	0x4002161C	FULL	Slave attributes 3
PERI_MS_PPU_FX56_MS_ADDR	0x40021620	FULL	Master region, base address
PERI_MS_PPU_FX56_MS_SIZE	0x40021624	FULL	Master region, size
PERI_MS_PPU_FX56_MS_ATT0	0x40021630	FULL	Master attributes 0
PERI_MS_PPU_FX56_MS_ATT1	0x40021634	FULL	Master attributes 1
PERI_MS_PPU_FX56_MS_ATT2	0x40021638	FULL	Master attributes 2
PERI_MS_PPU_FX56_MS_ATT3	0x4002163C	FULL	Master attributes 3

21.74 PPU_FX 57

Register Name	Address	Permission	Description
PERI_MS_PPU_FX57_SL_ADDR	0x40021640	FULL	Slave region, base address
PERI_MS_PPU_FX57_SL_SIZE	0x40021644	FULL	Slave region, size
PERI_MS_PPU_FX57_SL_ATT0	0x40021650	FULL	Slave attributes 0
PERI_MS_PPU_FX57_SL_ATT1	0x40021654	FULL	Slave attributes 1
PERI_MS_PPU_FX57_SL_ATT2	0x40021658	FULL	Slave attributes 2
PERI_MS_PPU_FX57_SL_ATT3	0x4002165C	FULL	Slave attributes 3
PERI_MS_PPU_FX57_MS_ADDR	0x40021660	FULL	Master region, base address
PERI_MS_PPU_FX57_MS_SIZE	0x40021664	FULL	Master region, size
PERI_MS_PPU_FX57_MS_ATT0	0x40021670	FULL	Master attributes 0
PERI_MS_PPU_FX57_MS_ATT1	0x40021674	FULL	Master attributes 1
PERI_MS_PPU_FX57_MS_ATT2	0x40021678	FULL	Master attributes 2
PERI_MS_PPU_FX57_MS_ATT3	0x4002167C	FULL	Master attributes 3

21.75 PPU_FX 58

Register Name	Address	Permission	Description
PERI_MS_PPU_FX58_SL_ADDR	0x40021680	FULL	Slave region, base address
PERI_MS_PPU_FX58_SL_SIZE	0x40021684	FULL	Slave region, size
PERI_MS_PPU_FX58_SL_ATT0	0x40021690	FULL	Slave attributes 0
PERI_MS_PPU_FX58_SL_ATT1	0x40021694	FULL	Slave attributes 1
PERI_MS_PPU_FX58_SL_ATT2	0x40021698	FULL	Slave attributes 2
PERI_MS_PPU_FX58_SL_ATT3	0x4002169C	FULL	Slave attributes 3
PERI_MS_PPU_FX58_MS_ADDR	0x400216A0	FULL	Master region, base address
PERI_MS_PPU_FX58_MS_SIZE	0x400216A4	FULL	Master region, size
PERI_MS_PPU_FX58_MS_ATT0	0x400216B0	FULL	Master attributes 0
PERI_MS_PPU_FX58_MS_ATT1	0x400216B4	FULL	Master attributes 1
PERI_MS_PPU_FX58_MS_ATT2	0x400216B8	FULL	Master attributes 2
PERI_MS_PPU_FX58_MS_ATT3	0x400216BC	FULL	Master attributes 3

21.76 PPU_FX 59

Register Name	Address	Permission	Description
PERI_MS_PPU_FX59_SL_ADDR	0x400216C0	FULL	Slave region, base address
PERI_MS_PPU_FX59_SL_SIZE	0x400216C4	FULL	Slave region, size
PERI_MS_PPU_FX59_SL_ATT0	0x400216D0	FULL	Slave attributes 0
PERI_MS_PPU_FX59_SL_ATT1	0x400216D4	FULL	Slave attributes 1
PERI_MS_PPU_FX59_SL_ATT2	0x400216D8	FULL	Slave attributes 2
PERI_MS_PPU_FX59_SL_ATT3	0x400216DC	FULL	Slave attributes 3
PERI_MS_PPU_FX59_MS_ADDR	0x400216E0	FULL	Master region, base address
PERI_MS_PPU_FX59_MS_SIZE	0x400216E4	FULL	Master region, size
PERI_MS_PPU_FX59_MS_ATT0	0x400216F0	FULL	Master attributes 0
PERI_MS_PPU_FX59_MS_ATT1	0x400216F4	FULL	Master attributes 1
PERI_MS_PPU_FX59_MS_ATT2	0x400216F8	FULL	Master attributes 2
PERI_MS_PPU_FX59_MS_ATT3	0x400216FC	FULL	Master attributes 3

21.77 PPU_FX 60

Register Name	Address	Permission	Description
PERI_MS_PPU_FX60_SL_ADDR	0x40021700	FULL	Slave region, base address
PERI_MS_PPU_FX60_SL_SIZE	0x40021704	FULL	Slave region, size
PERI_MS_PPU_FX60_SL_ATT0	0x40021710	FULL	Slave attributes 0
PERI_MS_PPU_FX60_SL_ATT1	0x40021714	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX60_SL_ATT2	0x40021718	FULL	Slave attributes 2
PERI_MS_PPU_FX60_SL_ATT3	0x4002171C	FULL	Slave attributes 3
PERI_MS_PPU_FX60_MS_ADDR	0x40021720	FULL	Master region, base address
PERI_MS_PPU_FX60_MS_SIZE	0x40021724	FULL	Master region, size
PERI_MS_PPU_FX60_MS_ATT0	0x40021730	FULL	Master attributes 0
PERI_MS_PPU_FX60_MS_ATT1	0x40021734	FULL	Master attributes 1
PERI_MS_PPU_FX60_MS_ATT2	0x40021738	FULL	Master attributes 2
PERI_MS_PPU_FX60_MS_ATT3	0x4002173C	FULL	Master attributes 3

21.78 PPU_FX 61

Register Name	Address	Permission	Description
PERI_MS_PPU_FX61_SL_ADDR	0x40021740	FULL	Slave region, base address
PERI_MS_PPU_FX61_SL_SIZE	0x40021744	FULL	Slave region, size
PERI_MS_PPU_FX61_SL_ATT0	0x40021750	FULL	Slave attributes 0
PERI_MS_PPU_FX61_SL_ATT1	0x40021754	FULL	Slave attributes 1
PERI_MS_PPU_FX61_SL_ATT2	0x40021758	FULL	Slave attributes 2
PERI_MS_PPU_FX61_SL_ATT3	0x4002175C	FULL	Slave attributes 3
PERI_MS_PPU_FX61_MS_ADDR	0x40021760	FULL	Master region, base address
PERI_MS_PPU_FX61_MS_SIZE	0x40021764	FULL	Master region, size
PERI_MS_PPU_FX61_MS_ATT0	0x40021770	FULL	Master attributes 0
PERI_MS_PPU_FX61_MS_ATT1	0x40021774	FULL	Master attributes 1
PERI_MS_PPU_FX61_MS_ATT2	0x40021778	FULL	Master attributes 2
PERI_MS_PPU_FX61_MS_ATT3	0x4002177C	FULL	Master attributes 3

21.79 PPU_FX 62

Register Name	Address	Permission	Description
PERI_MS_PPU_FX62_SL_ADDR	0x40021780	FULL	Slave region, base address
PERI_MS_PPU_FX62_SL_SIZE	0x40021784	FULL	Slave region, size
PERI_MS_PPU_FX62_SL_ATT0	0x40021790	FULL	Slave attributes 0
PERI_MS_PPU_FX62_SL_ATT1	0x40021794	FULL	Slave attributes 1
PERI_MS_PPU_FX62_SL_ATT2	0x40021798	FULL	Slave attributes 2
PERI_MS_PPU_FX62_SL_ATT3	0x4002179C	FULL	Slave attributes 3
PERI_MS_PPU_FX62_MS_ADDR	0x400217A0	FULL	Master region, base address
PERI_MS_PPU_FX62_MS_SIZE	0x400217A4	FULL	Master region, size
PERI_MS_PPU_FX62_MS_ATT0	0x400217B0	FULL	Master attributes 0
PERI_MS_PPU_FX62_MS_ATT1	0x400217B4	FULL	Master attributes 1
PERI_MS_PPU_FX62_MS_ATT2	0x400217B8	FULL	Master attributes 2
PERI_MS_PPU_FX62_MS_ATT3	0x400217BC	FULL	Master attributes 3

21.80 PPU_FX 63

Register Name	Address	Permission	Description
PERI_MS_PPU_FX63_SL_ADDR	0x400217C0	FULL	Slave region, base address
PERI_MS_PPU_FX63_SL_SIZE	0x400217C4	FULL	Slave region, size
PERI_MS_PPU_FX63_SL_ATT0	0x400217D0	FULL	Slave attributes 0
PERI_MS_PPU_FX63_SL_ATT1	0x400217D4	FULL	Slave attributes 1
PERI_MS_PPU_FX63_SL_ATT2	0x400217D8	FULL	Slave attributes 2
PERI_MS_PPU_FX63_SL_ATT3	0x400217DC	FULL	Slave attributes 3
PERI_MS_PPU_FX63_MS_ADDR	0x400217E0	FULL	Master region, base address
PERI_MS_PPU_FX63_MS_SIZE	0x400217E4	FULL	Master region, size
PERI_MS_PPU_FX63_MS_ATT0	0x400217F0	FULL	Master attributes 0
PERI_MS_PPU_FX63_MS_ATT1	0x400217F4	FULL	Master attributes 1
PERI_MS_PPU_FX63_MS_ATT2	0x400217F8	FULL	Master attributes 2
PERI_MS_PPU_FX63_MS_ATT3	0x400217FC	FULL	Master attributes 3

21.81 PPU_FX 64

Register Name	Address	Permission	Description
PERI_MS_PPU_FX64_SL_ADDR	0x40021800	FULL	Slave region, base address
PERI_MS_PPU_FX64_SL_SIZE	0x40021804	FULL	Slave region, size
PERI_MS_PPU_FX64_SL_ATT0	0x40021810	FULL	Slave attributes 0
PERI_MS_PPU_FX64_SL_ATT1	0x40021814	FULL	Slave attributes 1
PERI_MS_PPU_FX64_SL_ATT2	0x40021818	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX64_SL_ATT3	0x4002181C	FULL	Slave attributes 3
PERI_MS_PPU_FX64_MS_ADDR	0x40021820	FULL	Master region, base address
PERI_MS_PPU_FX64_MS_SIZE	0x40021824	FULL	Master region, size
PERI_MS_PPU_FX64_MS_ATT0	0x40021830	FULL	Master attributes 0
PERI_MS_PPU_FX64_MS_ATT1	0x40021834	FULL	Master attributes 1
PERI_MS_PPU_FX64_MS_ATT2	0x40021838	FULL	Master attributes 2
PERI_MS_PPU_FX64_MS_ATT3	0x4002183C	FULL	Master attributes 3

21.82 PPU_FX 65

Register Name	Address	Permission	Description
PERI_MS_PPU_FX65_SL_ADDR	0x40021840	READ	Slave region, base address
PERI_MS_PPU_FX65_SL_SIZE	0x40021844	READ	Slave region, size
PERI_MS_PPU_FX65_SL_ATT0	0x40021850	READ	Slave attributes 0
PERI_MS_PPU_FX65_SL_ATT1	0x40021854	READ	Slave attributes 1
PERI_MS_PPU_FX65_SL_ATT2	0x40021858	READ	Slave attributes 2
PERI_MS_PPU_FX65_SL_ATT3	0x4002185C	READ	Slave attributes 3
PERI_MS_PPU_FX65_MS_ADDR	0x40021860	READ	Master region, base address
PERI_MS_PPU_FX65_MS_SIZE	0x40021864	READ	Master region, size
PERI_MS_PPU_FX65_MS_ATT0	0x40021870	READ	Master attributes 0
PERI_MS_PPU_FX65_MS_ATT1	0x40021874	READ	Master attributes 1
PERI_MS_PPU_FX65_MS_ATT2	0x40021878	READ	Master attributes 2
PERI_MS_PPU_FX65_MS_ATT3	0x4002187C	READ	Master attributes 3

21.83 PPU_FX 66

Register Name	Address	Permission	Description
PERI_MS_PPU_FX66_SL_ADDR	0x40021880	FULL	Slave region, base address
PERI_MS_PPU_FX66_SL_SIZE	0x40021884	FULL	Slave region, size
PERI_MS_PPU_FX66_SL_ATT0	0x40021890	FULL	Slave attributes 0
PERI_MS_PPU_FX66_SL_ATT1	0x40021894	FULL	Slave attributes 1
PERI_MS_PPU_FX66_SL_ATT2	0x40021898	FULL	Slave attributes 2
PERI_MS_PPU_FX66_SL_ATT3	0x4002189C	FULL	Slave attributes 3
PERI_MS_PPU_FX66_MS_ADDR	0x400218A0	FULL	Master region, base address
PERI_MS_PPU_FX66_MS_SIZE	0x400218A4	FULL	Master region, size
PERI_MS_PPU_FX66_MS_ATT0	0x400218B0	FULL	Master attributes 0
PERI_MS_PPU_FX66_MS_ATT1	0x400218B4	FULL	Master attributes 1
PERI_MS_PPU_FX66_MS_ATT2	0x400218B8	FULL	Master attributes 2
PERI_MS_PPU_FX66_MS_ATT3	0x400218BC	FULL	Master attributes 3

21.84 PPU_FX 67

Register Name	Address	Permission	Description
PERI_MS_PPU_FX67_SL_ADDR	0x400218C0	FULL	Slave region, base address
PERI_MS_PPU_FX67_SL_SIZE	0x400218C4	FULL	Slave region, size
PERI_MS_PPU_FX67_SL_ATT0	0x400218D0	FULL	Slave attributes 0
PERI_MS_PPU_FX67_SL_ATT1	0x400218D4	FULL	Slave attributes 1
PERI_MS_PPU_FX67_SL_ATT2	0x400218D8	FULL	Slave attributes 2
PERI_MS_PPU_FX67_SL_ATT3	0x400218DC	FULL	Slave attributes 3
PERI_MS_PPU_FX67_MS_ADDR	0x400218E0	FULL	Master region, base address
PERI_MS_PPU_FX67_MS_SIZE	0x400218E4	FULL	Master region, size
PERI_MS_PPU_FX67_MS_ATT0	0x400218F0	FULL	Master attributes 0
PERI_MS_PPU_FX67_MS_ATT1	0x400218F4	FULL	Master attributes 1
PERI_MS_PPU_FX67_MS_ATT2	0x400218F8	FULL	Master attributes 2
PERI_MS_PPU_FX67_MS_ATT3	0x400218FC	FULL	Master attributes 3

21.85 PPU_FX 68

Register Name	Address	Permission	Description
PERI_MS_PPU_FX68_SL_ADDR	0x40021900	FULL	Slave region, base address
PERI_MS_PPU_FX68_SL_SIZE	0x40021904	FULL	Slave region, size
PERI_MS_PPU_FX68_SL_ATT0	0x40021910	FULL	Slave attributes 0
PERI_MS_PPU_FX68_SL_ATT1	0x40021914	FULL	Slave attributes 1
PERI_MS_PPU_FX68_SL_ATT2	0x40021918	FULL	Slave attributes 2
PERI_MS_PPU_FX68_SL_ATT3	0x4002191C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX68_MS_ADDR	0x40021920	FULL	Master region, base address
PERI_MS_PPU_FX68_MS_SIZE	0x40021924	FULL	Master region, size
PERI_MS_PPU_FX68_MS_ATT0	0x40021930	FULL	Master attributes 0
PERI_MS_PPU_FX68_MS_ATT1	0x40021934	FULL	Master attributes 1
PERI_MS_PPU_FX68_MS_ATT2	0x40021938	FULL	Master attributes 2
PERI_MS_PPU_FX68_MS_ATT3	0x4002193C	FULL	Master attributes 3

21.86 PPU_FX 69

Register Name	Address	Permission	Description
PERI_MS_PPU_FX69_SL_ADDR	0x40021940	FULL	Slave region, base address
PERI_MS_PPU_FX69_SL_SIZE	0x40021944	FULL	Slave region, size
PERI_MS_PPU_FX69_SL_ATT0	0x40021950	FULL	Slave attributes 0
PERI_MS_PPU_FX69_SL_ATT1	0x40021954	FULL	Slave attributes 1
PERI_MS_PPU_FX69_SL_ATT2	0x40021958	FULL	Slave attributes 2
PERI_MS_PPU_FX69_SL_ATT3	0x4002195C	FULL	Slave attributes 3
PERI_MS_PPU_FX69_MS_ADDR	0x40021960	FULL	Master region, base address
PERI_MS_PPU_FX69_MS_SIZE	0x40021964	FULL	Master region, size
PERI_MS_PPU_FX69_MS_ATT0	0x40021970	FULL	Master attributes 0
PERI_MS_PPU_FX69_MS_ATT1	0x40021974	FULL	Master attributes 1
PERI_MS_PPU_FX69_MS_ATT2	0x40021978	FULL	Master attributes 2
PERI_MS_PPU_FX69_MS_ATT3	0x4002197C	FULL	Master attributes 3

21.87 PPU_FX 70

Register Name	Address	Permission	Description
PERI_MS_PPU_FX70_SL_ADDR	0x40021980	FULL	Slave region, base address
PERI_MS_PPU_FX70_SL_SIZE	0x40021984	FULL	Slave region, size
PERI_MS_PPU_FX70_SL_ATT0	0x40021990	FULL	Slave attributes 0
PERI_MS_PPU_FX70_SL_ATT1	0x40021994	FULL	Slave attributes 1
PERI_MS_PPU_FX70_SL_ATT2	0x40021998	FULL	Slave attributes 2
PERI_MS_PPU_FX70_SL_ATT3	0x4002199C	FULL	Slave attributes 3
PERI_MS_PPU_FX70_MS_ADDR	0x400219A0	FULL	Master region, base address
PERI_MS_PPU_FX70_MS_SIZE	0x400219A4	FULL	Master region, size
PERI_MS_PPU_FX70_MS_ATT0	0x400219B0	FULL	Master attributes 0
PERI_MS_PPU_FX70_MS_ATT1	0x400219B4	FULL	Master attributes 1
PERI_MS_PPU_FX70_MS_ATT2	0x400219B8	FULL	Master attributes 2
PERI_MS_PPU_FX70_MS_ATT3	0x400219BC	FULL	Master attributes 3

21.88 PPU_FX 71

Register Name	Address	Permission	Description
PERI_MS_PPU_FX71_SL_ADDR	0x400219C0	FULL	Slave region, base address
PERI_MS_PPU_FX71_SL_SIZE	0x400219C4	FULL	Slave region, size
PERI_MS_PPU_FX71_SL_ATT0	0x400219D0	FULL	Slave attributes 0
PERI_MS_PPU_FX71_SL_ATT1	0x400219D4	FULL	Slave attributes 1
PERI_MS_PPU_FX71_SL_ATT2	0x400219D8	FULL	Slave attributes 2
PERI_MS_PPU_FX71_SL_ATT3	0x400219DC	FULL	Slave attributes 3
PERI_MS_PPU_FX71_MS_ADDR	0x400219E0	FULL	Master region, base address
PERI_MS_PPU_FX71_MS_SIZE	0x400219E4	FULL	Master region, size
PERI_MS_PPU_FX71_MS_ATT0	0x400219F0	FULL	Master attributes 0
PERI_MS_PPU_FX71_MS_ATT1	0x400219F4	FULL	Master attributes 1
PERI_MS_PPU_FX71_MS_ATT2	0x400219F8	FULL	Master attributes 2
PERI_MS_PPU_FX71_MS_ATT3	0x400219FC	FULL	Master attributes 3

21.89 PPU_FX 72

Register Name	Address	Permission	Description
PERI_MS_PPU_FX72_SL_ADDR	0x40021A00	FULL	Slave region, base address
PERI_MS_PPU_FX72_SL_SIZE	0x40021A04	FULL	Slave region, size
PERI_MS_PPU_FX72_SL_ATT0	0x40021A10	FULL	Slave attributes 0
PERI_MS_PPU_FX72_SL_ATT1	0x40021A14	FULL	Slave attributes 1
PERI_MS_PPU_FX72_SL_ATT2	0x40021A18	FULL	Slave attributes 2
PERI_MS_PPU_FX72_SL_ATT3	0x40021A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX72_MS_ADDR	0x40021A20	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX72_MS_SIZE	0x40021A24	FULL	Master region, size
PERI_MS_PPU_FX72_MS_ATT0	0x40021A30	FULL	Master attributes 0
PERI_MS_PPU_FX72_MS_ATT1	0x40021A34	FULL	Master attributes 1
PERI_MS_PPU_FX72_MS_ATT2	0x40021A38	FULL	Master attributes 2
PERI_MS_PPU_FX72_MS_ATT3	0x40021A3C	FULL	Master attributes 3

21.90 PPU_FX 73

Register Name	Address	Permission	Description
PERI_MS_PPU_FX73_SL_ADDR	0x40021A40	FULL	Slave region, base address
PERI_MS_PPU_FX73_SL_SIZE	0x40021A44	FULL	Slave region, size
PERI_MS_PPU_FX73_SL_ATT0	0x40021A50	FULL	Slave attributes 0
PERI_MS_PPU_FX73_SL_ATT1	0x40021A54	FULL	Slave attributes 1
PERI_MS_PPU_FX73_SL_ATT2	0x40021A58	FULL	Slave attributes 2
PERI_MS_PPU_FX73_SL_ATT3	0x40021A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX73_MS_ADDR	0x40021A60	FULL	Master region, base address
PERI_MS_PPU_FX73_MS_SIZE	0x40021A64	FULL	Master region, size
PERI_MS_PPU_FX73_MS_ATT0	0x40021A70	FULL	Master attributes 0
PERI_MS_PPU_FX73_MS_ATT1	0x40021A74	FULL	Master attributes 1
PERI_MS_PPU_FX73_MS_ATT2	0x40021A78	FULL	Master attributes 2
PERI_MS_PPU_FX73_MS_ATT3	0x40021A7C	FULL	Master attributes 3

21.91 PPU_FX 74

Register Name	Address	Permission	Description
PERI_MS_PPU_FX74_SL_ADDR	0x40021A80	FULL	Slave region, base address
PERI_MS_PPU_FX74_SL_SIZE	0x40021A84	FULL	Slave region, size
PERI_MS_PPU_FX74_SL_ATT0	0x40021A90	FULL	Slave attributes 0
PERI_MS_PPU_FX74_SL_ATT1	0x40021A94	FULL	Slave attributes 1
PERI_MS_PPU_FX74_SL_ATT2	0x40021A98	FULL	Slave attributes 2
PERI_MS_PPU_FX74_SL_ATT3	0x40021A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX74_MS_ADDR	0x40021AA0	FULL	Master region, base address
PERI_MS_PPU_FX74_MS_SIZE	0x40021AA4	FULL	Master region, size
PERI_MS_PPU_FX74_MS_ATT0	0x40021AB0	FULL	Master attributes 0
PERI_MS_PPU_FX74_MS_ATT1	0x40021AB4	FULL	Master attributes 1
PERI_MS_PPU_FX74_MS_ATT2	0x40021AB8	FULL	Master attributes 2
PERI_MS_PPU_FX74_MS_ATT3	0x40021ABC	FULL	Master attributes 3

21.92 PPU_FX 75

Register Name	Address	Permission	Description
PERI_MS_PPU_FX75_SL_ADDR	0x40021AC0	READ	Slave region, base address
PERI_MS_PPU_FX75_SL_SIZE	0x40021AC4	READ	Slave region, size
PERI_MS_PPU_FX75_SL_ATT0	0x40021AD0	READ	Slave attributes 0
PERI_MS_PPU_FX75_SL_ATT1	0x40021AD4	READ	Slave attributes 1
PERI_MS_PPU_FX75_SL_ATT2	0x40021AD8	READ	Slave attributes 2
PERI_MS_PPU_FX75_SL_ATT3	0x40021ADC	READ	Slave attributes 3
PERI_MS_PPU_FX75_MS_ADDR	0x40021AE0	READ	Master region, base address
PERI_MS_PPU_FX75_MS_SIZE	0x40021AE4	READ	Master region, size
PERI_MS_PPU_FX75_MS_ATT0	0x40021AF0	READ	Master attributes 0
PERI_MS_PPU_FX75_MS_ATT1	0x40021AF4	READ	Master attributes 1
PERI_MS_PPU_FX75_MS_ATT2	0x40021AF8	READ	Master attributes 2
PERI_MS_PPU_FX75_MS_ATT3	0x40021AFC	READ	Master attributes 3

21.93 PPU_FX 76

Register Name	Address	Permission	Description
PERI_MS_PPU_FX76_SL_ADDR	0x40021B00	FULL	Slave region, base address
PERI_MS_PPU_FX76_SL_SIZE	0x40021B04	FULL	Slave region, size
PERI_MS_PPU_FX76_SL_ATT0	0x40021B10	FULL	Slave attributes 0
PERI_MS_PPU_FX76_SL_ATT1	0x40021B14	FULL	Slave attributes 1
PERI_MS_PPU_FX76_SL_ATT2	0x40021B18	FULL	Slave attributes 2
PERI_MS_PPU_FX76_SL_ATT3	0x40021B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX76_MS_ADDR	0x40021B20	FULL	Master region, base address
PERI_MS_PPU_FX76_MS_SIZE	0x40021B24	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX76_MS_ATT0	0x40021B30	FULL	Master attributes 0
PERI_MS_PPU_FX76_MS_ATT1	0x40021B34	FULL	Master attributes 1
PERI_MS_PPU_FX76_MS_ATT2	0x40021B38	FULL	Master attributes 2
PERI_MS_PPU_FX76_MS_ATT3	0x40021B3C	FULL	Master attributes 3

21.94 PPU_FX 77

Register Name	Address	Permission	Description
PERI_MS_PPU_FX77_SL_ADDR	0x40021B40	FULL	Slave region, base address
PERI_MS_PPU_FX77_SL_SIZE	0x40021B44	FULL	Slave region, size
PERI_MS_PPU_FX77_SL_ATT0	0x40021B50	FULL	Slave attributes 0
PERI_MS_PPU_FX77_SL_ATT1	0x40021B54	FULL	Slave attributes 1
PERI_MS_PPU_FX77_SL_ATT2	0x40021B58	FULL	Slave attributes 2
PERI_MS_PPU_FX77_SL_ATT3	0x40021B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX77_MS_ADDR	0x40021B60	FULL	Master region, base address
PERI_MS_PPU_FX77_MS_SIZE	0x40021B64	FULL	Master region, size
PERI_MS_PPU_FX77_MS_ATT0	0x40021B70	FULL	Master attributes 0
PERI_MS_PPU_FX77_MS_ATT1	0x40021B74	FULL	Master attributes 1
PERI_MS_PPU_FX77_MS_ATT2	0x40021B78	FULL	Master attributes 2
PERI_MS_PPU_FX77_MS_ATT3	0x40021B7C	FULL	Master attributes 3

21.95 PPU_FX 78

Register Name	Address	Permission	Description
PERI_MS_PPU_FX78_SL_ADDR	0x40021B80	FULL	Slave region, base address
PERI_MS_PPU_FX78_SL_SIZE	0x40021B84	FULL	Slave region, size
PERI_MS_PPU_FX78_SL_ATT0	0x40021B90	FULL	Slave attributes 0
PERI_MS_PPU_FX78_SL_ATT1	0x40021B94	FULL	Slave attributes 1
PERI_MS_PPU_FX78_SL_ATT2	0x40021B98	FULL	Slave attributes 2
PERI_MS_PPU_FX78_SL_ATT3	0x40021B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX78_MS_ADDR	0x40021BA0	FULL	Master region, base address
PERI_MS_PPU_FX78_MS_SIZE	0x40021BA4	FULL	Master region, size
PERI_MS_PPU_FX78_MS_ATT0	0x40021BB0	FULL	Master attributes 0
PERI_MS_PPU_FX78_MS_ATT1	0x40021BB4	FULL	Master attributes 1
PERI_MS_PPU_FX78_MS_ATT2	0x40021BB8	FULL	Master attributes 2
PERI_MS_PPU_FX78_MS_ATT3	0x40021BBC	FULL	Master attributes 3

21.96 PPU_FX 79

Register Name	Address	Permission	Description
PERI_MS_PPU_FX79_SL_ADDR	0x40021BC0	FULL	Slave region, base address
PERI_MS_PPU_FX79_SL_SIZE	0x40021BC4	FULL	Slave region, size
PERI_MS_PPU_FX79_SL_ATT0	0x40021BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX79_SL_ATT1	0x40021BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX79_SL_ATT2	0x40021BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX79_SL_ATT3	0x40021BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX79_MS_ADDR	0x40021BE0	FULL	Master region, base address
PERI_MS_PPU_FX79_MS_SIZE	0x40021BE4	FULL	Master region, size
PERI_MS_PPU_FX79_MS_ATT0	0x40021BF0	FULL	Master attributes 0
PERI_MS_PPU_FX79_MS_ATT1	0x40021BF4	FULL	Master attributes 1
PERI_MS_PPU_FX79_MS_ATT2	0x40021BF8	FULL	Master attributes 2
PERI_MS_PPU_FX79_MS_ATT3	0x40021BFC	FULL	Master attributes 3

21.97 PPU_FX 80

Register Name	Address	Permission	Description
PERI_MS_PPU_FX80_SL_ADDR	0x40021C00	READ	Slave region, base address
PERI_MS_PPU_FX80_SL_SIZE	0x40021C04	READ	Slave region, size
PERI_MS_PPU_FX80_SL_ATT0	0x40021C10	READ	Slave attributes 0
PERI_MS_PPU_FX80_SL_ATT1	0x40021C14	READ	Slave attributes 1
PERI_MS_PPU_FX80_SL_ATT2	0x40021C18	READ	Slave attributes 2
PERI_MS_PPU_FX80_SL_ATT3	0x40021C1C	READ	Slave attributes 3
PERI_MS_PPU_FX80_MS_ADDR	0x40021C20	READ	Master region, base address
PERI_MS_PPU_FX80_MS_SIZE	0x40021C24	READ	Master region, size
PERI_MS_PPU_FX80_MS_ATT0	0x40021C30	READ	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX80_MS_ATT1	0x40021C34	READ	Master attributes 1
PERI_MS_PPU_FX80_MS_ATT2	0x40021C38	READ	Master attributes 2
PERI_MS_PPU_FX80_MS_ATT3	0x40021C3C	READ	Master attributes 3

21.98 PPU_FX 81

Register Name	Address	Permission	Description
PERI_MS_PPU_FX81_SL_ADDR	0x40021C40	FULL	Slave region, base address
PERI_MS_PPU_FX81_SL_SIZE	0x40021C44	FULL	Slave region, size
PERI_MS_PPU_FX81_SL_ATT0	0x40021C50	FULL	Slave attributes 0
PERI_MS_PPU_FX81_SL_ATT1	0x40021C54	FULL	Slave attributes 1
PERI_MS_PPU_FX81_SL_ATT2	0x40021C58	FULL	Slave attributes 2
PERI_MS_PPU_FX81_SL_ATT3	0x40021C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX81_MS_ADDR	0x40021C60	FULL	Master region, base address
PERI_MS_PPU_FX81_MS_SIZE	0x40021C64	FULL	Master region, size
PERI_MS_PPU_FX81_MS_ATT0	0x40021C70	FULL	Master attributes 0
PERI_MS_PPU_FX81_MS_ATT1	0x40021C74	FULL	Master attributes 1
PERI_MS_PPU_FX81_MS_ATT2	0x40021C78	FULL	Master attributes 2
PERI_MS_PPU_FX81_MS_ATT3	0x40021C7C	FULL	Master attributes 3

21.99 PPU_FX 82

Register Name	Address	Permission	Description
PERI_MS_PPU_FX82_SL_ADDR	0x40021C80	FULL	Slave region, base address
PERI_MS_PPU_FX82_SL_SIZE	0x40021C84	FULL	Slave region, size
PERI_MS_PPU_FX82_SL_ATT0	0x40021C90	FULL	Slave attributes 0
PERI_MS_PPU_FX82_SL_ATT1	0x40021C94	FULL	Slave attributes 1
PERI_MS_PPU_FX82_SL_ATT2	0x40021C98	FULL	Slave attributes 2
PERI_MS_PPU_FX82_SL_ATT3	0x40021C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX82_MS_ADDR	0x40021CA0	FULL	Master region, base address
PERI_MS_PPU_FX82_MS_SIZE	0x40021CA4	FULL	Master region, size
PERI_MS_PPU_FX82_MS_ATT0	0x40021CB0	FULL	Master attributes 0
PERI_MS_PPU_FX82_MS_ATT1	0x40021CB4	FULL	Master attributes 1
PERI_MS_PPU_FX82_MS_ATT2	0x40021CB8	FULL	Master attributes 2
PERI_MS_PPU_FX82_MS_ATT3	0x40021CBC	FULL	Master attributes 3

21.100 PPU_FX 83

Register Name	Address	Permission	Description
PERI_MS_PPU_FX83_SL_ADDR	0x40021CC0	FULL	Slave region, base address
PERI_MS_PPU_FX83_SL_SIZE	0x40021CC4	FULL	Slave region, size
PERI_MS_PPU_FX83_SL_ATT0	0x40021CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX83_SL_ATT1	0x40021CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX83_SL_ATT2	0x40021CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX83_SL_ATT3	0x40021CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX83_MS_ADDR	0x40021CE0	FULL	Master region, base address
PERI_MS_PPU_FX83_MS_SIZE	0x40021CE4	FULL	Master region, size
PERI_MS_PPU_FX83_MS_ATT0	0x40021CF0	FULL	Master attributes 0
PERI_MS_PPU_FX83_MS_ATT1	0x40021CF4	FULL	Master attributes 1
PERI_MS_PPU_FX83_MS_ATT2	0x40021CF8	FULL	Master attributes 2
PERI_MS_PPU_FX83_MS_ATT3	0x40021CFC	FULL	Master attributes 3

21.101 PPU_FX 84

Register Name	Address	Permission	Description
PERI_MS_PPU_FX84_SL_ADDR	0x40021D00	FULL	Slave region, base address
PERI_MS_PPU_FX84_SL_SIZE	0x40021D04	FULL	Slave region, size
PERI_MS_PPU_FX84_SL_ATT0	0x40021D10	FULL	Slave attributes 0
PERI_MS_PPU_FX84_SL_ATT1	0x40021D14	FULL	Slave attributes 1
PERI_MS_PPU_FX84_SL_ATT2	0x40021D18	FULL	Slave attributes 2
PERI_MS_PPU_FX84_SL_ATT3	0x40021D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX84_MS_ADDR	0x40021D20	FULL	Master region, base address
PERI_MS_PPU_FX84_MS_SIZE	0x40021D24	FULL	Master region, size
PERI_MS_PPU_FX84_MS_ATT0	0x40021D30	FULL	Master attributes 0
PERI_MS_PPU_FX84_MS_ATT1	0x40021D34	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX84_MS_ATT2	0x40021D38	FULL	Master attributes 2
PERI_MS_PPU_FX84_MS_ATT3	0x40021D3C	FULL	Master attributes 3

21.102 PPU_FX 85

Register Name	Address	Permission	Description
PERI_MS_PPU_FX85_SL_ADDR	0x40021D40	FULL	Slave region, base address
PERI_MS_PPU_FX85_SL_SIZE	0x40021D44	FULL	Slave region, size
PERI_MS_PPU_FX85_SL_ATT0	0x40021D50	FULL	Slave attributes 0
PERI_MS_PPU_FX85_SL_ATT1	0x40021D54	FULL	Slave attributes 1
PERI_MS_PPU_FX85_SL_ATT2	0x40021D58	FULL	Slave attributes 2
PERI_MS_PPU_FX85_SL_ATT3	0x40021D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX85_MS_ADDR	0x40021D60	FULL	Master region, base address
PERI_MS_PPU_FX85_MS_SIZE	0x40021D64	FULL	Master region, size
PERI_MS_PPU_FX85_MS_ATT0	0x40021D70	FULL	Master attributes 0
PERI_MS_PPU_FX85_MS_ATT1	0x40021D74	FULL	Master attributes 1
PERI_MS_PPU_FX85_MS_ATT2	0x40021D78	FULL	Master attributes 2
PERI_MS_PPU_FX85_MS_ATT3	0x40021D7C	FULL	Master attributes 3

21.103 PPU_FX 86

Register Name	Address	Permission	Description
PERI_MS_PPU_FX86_SL_ADDR	0x40021D80	FULL	Slave region, base address
PERI_MS_PPU_FX86_SL_SIZE	0x40021D84	FULL	Slave region, size
PERI_MS_PPU_FX86_SL_ATT0	0x40021D90	FULL	Slave attributes 0
PERI_MS_PPU_FX86_SL_ATT1	0x40021D94	FULL	Slave attributes 1
PERI_MS_PPU_FX86_SL_ATT2	0x40021D98	FULL	Slave attributes 2
PERI_MS_PPU_FX86_SL_ATT3	0x40021D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX86_MS_ADDR	0x40021DA0	FULL	Master region, base address
PERI_MS_PPU_FX86_MS_SIZE	0x40021DA4	FULL	Master region, size
PERI_MS_PPU_FX86_MS_ATT0	0x40021DB0	FULL	Master attributes 0
PERI_MS_PPU_FX86_MS_ATT1	0x40021DB4	FULL	Master attributes 1
PERI_MS_PPU_FX86_MS_ATT2	0x40021DB8	FULL	Master attributes 2
PERI_MS_PPU_FX86_MS_ATT3	0x40021DBC	FULL	Master attributes 3

21.104 PPU_FX 87

Register Name	Address	Permission	Description
PERI_MS_PPU_FX87_SL_ADDR	0x40021DC0	FULL	Slave region, base address
PERI_MS_PPU_FX87_SL_SIZE	0x40021DC4	FULL	Slave region, size
PERI_MS_PPU_FX87_SL_ATT0	0x40021DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX87_SL_ATT1	0x40021DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX87_SL_ATT2	0x40021DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX87_SL_ATT3	0x40021DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX87_MS_ADDR	0x40021DE0	FULL	Master region, base address
PERI_MS_PPU_FX87_MS_SIZE	0x40021DE4	FULL	Master region, size
PERI_MS_PPU_FX87_MS_ATT0	0x40021DF0	FULL	Master attributes 0
PERI_MS_PPU_FX87_MS_ATT1	0x40021DF4	FULL	Master attributes 1
PERI_MS_PPU_FX87_MS_ATT2	0x40021DF8	FULL	Master attributes 2
PERI_MS_PPU_FX87_MS_ATT3	0x40021DFC	FULL	Master attributes 3

21.105 PPU_FX 88

Register Name	Address	Permission	Description
PERI_MS_PPU_FX88_SL_ADDR	0x40021E00	FULL	Slave region, base address
PERI_MS_PPU_FX88_SL_SIZE	0x40021E04	FULL	Slave region, size
PERI_MS_PPU_FX88_SL_ATT0	0x40021E10	FULL	Slave attributes 0
PERI_MS_PPU_FX88_SL_ATT1	0x40021E14	FULL	Slave attributes 1
PERI_MS_PPU_FX88_SL_ATT2	0x40021E18	FULL	Slave attributes 2
PERI_MS_PPU_FX88_SL_ATT3	0x40021E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX88_MS_ADDR	0x40021E20	FULL	Master region, base address
PERI_MS_PPU_FX88_MS_SIZE	0x40021E24	FULL	Master region, size
PERI_MS_PPU_FX88_MS_ATT0	0x40021E30	FULL	Master attributes 0
PERI_MS_PPU_FX88_MS_ATT1	0x40021E34	FULL	Master attributes 1
PERI_MS_PPU_FX88_MS_ATT2	0x40021E38	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX88_MS_ATT3	0x40021E3C	FULL	Master attributes 3

21.106 PPU_FX 89

Register Name	Address	Permission	Description
PERI_MS_PPU_FX89_SL_ADDR	0x40021E40	FULL	Slave region, base address
PERI_MS_PPU_FX89_SL_SIZE	0x40021E44	FULL	Slave region, size
PERI_MS_PPU_FX89_SL_ATT0	0x40021E50	FULL	Slave attributes 0
PERI_MS_PPU_FX89_SL_ATT1	0x40021E54	FULL	Slave attributes 1
PERI_MS_PPU_FX89_SL_ATT2	0x40021E58	FULL	Slave attributes 2
PERI_MS_PPU_FX89_SL_ATT3	0x40021E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX89_MS_ADDR	0x40021E60	FULL	Master region, base address
PERI_MS_PPU_FX89_MS_SIZE	0x40021E64	FULL	Master region, size
PERI_MS_PPU_FX89_MS_ATT0	0x40021E70	FULL	Master attributes 0
PERI_MS_PPU_FX89_MS_ATT1	0x40021E74	FULL	Master attributes 1
PERI_MS_PPU_FX89_MS_ATT2	0x40021E78	FULL	Master attributes 2
PERI_MS_PPU_FX89_MS_ATT3	0x40021E7C	FULL	Master attributes 3

21.107 PPU_FX 90

Register Name	Address	Permission	Description
PERI_MS_PPU_FX90_SL_ADDR	0x40021E80	FULL	Slave region, base address
PERI_MS_PPU_FX90_SL_SIZE	0x40021E84	FULL	Slave region, size
PERI_MS_PPU_FX90_SL_ATT0	0x40021E90	FULL	Slave attributes 0
PERI_MS_PPU_FX90_SL_ATT1	0x40021E94	FULL	Slave attributes 1
PERI_MS_PPU_FX90_SL_ATT2	0x40021E98	FULL	Slave attributes 2
PERI_MS_PPU_FX90_SL_ATT3	0x40021E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX90_MS_ADDR	0x40021EA0	FULL	Master region, base address
PERI_MS_PPU_FX90_MS_SIZE	0x40021EA4	FULL	Master region, size
PERI_MS_PPU_FX90_MS_ATT0	0x40021EB0	FULL	Master attributes 0
PERI_MS_PPU_FX90_MS_ATT1	0x40021EB4	FULL	Master attributes 1
PERI_MS_PPU_FX90_MS_ATT2	0x40021EB8	FULL	Master attributes 2
PERI_MS_PPU_FX90_MS_ATT3	0x40021EBC	FULL	Master attributes 3

21.108 PPU_FX 91

Register Name	Address	Permission	Description
PERI_MS_PPU_FX91_SL_ADDR	0x40021EC0	FULL	Slave region, base address
PERI_MS_PPU_FX91_SL_SIZE	0x40021EC4	FULL	Slave region, size
PERI_MS_PPU_FX91_SL_ATT0	0x40021ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX91_SL_ATT1	0x40021ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX91_SL_ATT2	0x40021ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX91_SL_ATT3	0x40021EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX91_MS_ADDR	0x40021EE0	FULL	Master region, base address
PERI_MS_PPU_FX91_MS_SIZE	0x40021EE4	FULL	Master region, size
PERI_MS_PPU_FX91_MS_ATT0	0x40021EF0	FULL	Master attributes 0
PERI_MS_PPU_FX91_MS_ATT1	0x40021EF4	FULL	Master attributes 1
PERI_MS_PPU_FX91_MS_ATT2	0x40021EF8	FULL	Master attributes 2
PERI_MS_PPU_FX91_MS_ATT3	0x40021EFC	FULL	Master attributes 3

21.109 PPU_FX 92

Register Name	Address	Permission	Description
PERI_MS_PPU_FX92_SL_ADDR	0x40021F00	FULL	Slave region, base address
PERI_MS_PPU_FX92_SL_SIZE	0x40021F04	FULL	Slave region, size
PERI_MS_PPU_FX92_SL_ATT0	0x40021F10	FULL	Slave attributes 0
PERI_MS_PPU_FX92_SL_ATT1	0x40021F14	FULL	Slave attributes 1
PERI_MS_PPU_FX92_SL_ATT2	0x40021F18	FULL	Slave attributes 2
PERI_MS_PPU_FX92_SL_ATT3	0x40021F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX92_MS_ADDR	0x40021F20	FULL	Master region, base address
PERI_MS_PPU_FX92_MS_SIZE	0x40021F24	FULL	Master region, size
PERI_MS_PPU_FX92_MS_ATT0	0x40021F30	FULL	Master attributes 0
PERI_MS_PPU_FX92_MS_ATT1	0x40021F34	FULL	Master attributes 1
PERI_MS_PPU_FX92_MS_ATT2	0x40021F38	FULL	Master attributes 2
PERI_MS_PPU_FX92_MS_ATT3	0x40021F3C	FULL	Master attributes 3

21.110 PPU_FX 93

Register Name	Address	Permission	Description
PERI_MS_PPU_FX93_SL_ADDR	0x40021F40	FULL	Slave region, base address
PERI_MS_PPU_FX93_SL_SIZE	0x40021F44	FULL	Slave region, size
PERI_MS_PPU_FX93_SL_ATT0	0x40021F50	FULL	Slave attributes 0
PERI_MS_PPU_FX93_SL_ATT1	0x40021F54	FULL	Slave attributes 1
PERI_MS_PPU_FX93_SL_ATT2	0x40021F58	FULL	Slave attributes 2
PERI_MS_PPU_FX93_SL_ATT3	0x40021F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX93_MS_ADDR	0x40021F60	FULL	Master region, base address
PERI_MS_PPU_FX93_MS_SIZE	0x40021F64	FULL	Master region, size
PERI_MS_PPU_FX93_MS_ATT0	0x40021F70	FULL	Master attributes 0
PERI_MS_PPU_FX93_MS_ATT1	0x40021F74	FULL	Master attributes 1
PERI_MS_PPU_FX93_MS_ATT2	0x40021F78	FULL	Master attributes 2
PERI_MS_PPU_FX93_MS_ATT3	0x40021F7C	FULL	Master attributes 3

21.111 PPU_FX 94

Register Name	Address	Permission	Description
PERI_MS_PPU_FX94_SL_ADDR	0x40021F80	FULL	Slave region, base address
PERI_MS_PPU_FX94_SL_SIZE	0x40021F84	FULL	Slave region, size
PERI_MS_PPU_FX94_SL_ATT0	0x40021F90	FULL	Slave attributes 0
PERI_MS_PPU_FX94_SL_ATT1	0x40021F94	FULL	Slave attributes 1
PERI_MS_PPU_FX94_SL_ATT2	0x40021F98	FULL	Slave attributes 2
PERI_MS_PPU_FX94_SL_ATT3	0x40021F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX94_MS_ADDR	0x40021FA0	FULL	Master region, base address
PERI_MS_PPU_FX94_MS_SIZE	0x40021FA4	FULL	Master region, size
PERI_MS_PPU_FX94_MS_ATT0	0x40021FB0	FULL	Master attributes 0
PERI_MS_PPU_FX94_MS_ATT1	0x40021FB4	FULL	Master attributes 1
PERI_MS_PPU_FX94_MS_ATT2	0x40021FB8	FULL	Master attributes 2
PERI_MS_PPU_FX94_MS_ATT3	0x40021FBC	FULL	Master attributes 3

21.112 PPU_FX 95

Register Name	Address	Permission	Description
PERI_MS_PPU_FX95_SL_ADDR	0x40021FC0	FULL	Slave region, base address
PERI_MS_PPU_FX95_SL_SIZE	0x40021FC4	FULL	Slave region, size
PERI_MS_PPU_FX95_SL_ATT0	0x40021FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX95_SL_ATT1	0x40021FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX95_SL_ATT2	0x40021FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX95_SL_ATT3	0x40021FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX95_MS_ADDR	0x40021FE0	FULL	Master region, base address
PERI_MS_PPU_FX95_MS_SIZE	0x40021FE4	FULL	Master region, size
PERI_MS_PPU_FX95_MS_ATT0	0x40021FF0	FULL	Master attributes 0
PERI_MS_PPU_FX95_MS_ATT1	0x40021FF4	FULL	Master attributes 1
PERI_MS_PPU_FX95_MS_ATT2	0x40021FF8	FULL	Master attributes 2
PERI_MS_PPU_FX95_MS_ATT3	0x40021FFC	FULL	Master attributes 3

21.113 PPU_FX 96

Register Name	Address	Permission	Description
PERI_MS_PPU_FX96_SL_ADDR	0x40022000	FULL	Slave region, base address
PERI_MS_PPU_FX96_SL_SIZE	0x40022004	FULL	Slave region, size
PERI_MS_PPU_FX96_SL_ATT0	0x40022010	FULL	Slave attributes 0
PERI_MS_PPU_FX96_SL_ATT1	0x40022014	FULL	Slave attributes 1
PERI_MS_PPU_FX96_SL_ATT2	0x40022018	FULL	Slave attributes 2
PERI_MS_PPU_FX96_SL_ATT3	0x4002201C	FULL	Slave attributes 3
PERI_MS_PPU_FX96_MS_ADDR	0x40022020	FULL	Master region, base address
PERI_MS_PPU_FX96_MS_SIZE	0x40022024	FULL	Master region, size
PERI_MS_PPU_FX96_MS_ATT0	0x40022030	FULL	Master attributes 0
PERI_MS_PPU_FX96_MS_ATT1	0x40022034	FULL	Master attributes 1
PERI_MS_PPU_FX96_MS_ATT2	0x40022038	FULL	Master attributes 2
PERI_MS_PPU_FX96_MS_ATT3	0x4002203C	FULL	Master attributes 3

21.114 PPU_FX 97

Register Name	Address	Permission	Description
PERI_MS_PPU_FX97_SL_ADDR	0x40022040	FULL	Slave region, base address
PERI_MS_PPU_FX97_SL_SIZE	0x40022044	FULL	Slave region, size
PERI_MS_PPU_FX97_SL_ATT0	0x40022050	FULL	Slave attributes 0
PERI_MS_PPU_FX97_SL_ATT1	0x40022054	FULL	Slave attributes 1
PERI_MS_PPU_FX97_SL_ATT2	0x40022058	FULL	Slave attributes 2
PERI_MS_PPU_FX97_SL_ATT3	0x4002205C	FULL	Slave attributes 3
PERI_MS_PPU_FX97_MS_ADDR	0x40022060	FULL	Master region, base address
PERI_MS_PPU_FX97_MS_SIZE	0x40022064	FULL	Master region, size
PERI_MS_PPU_FX97_MS_ATT0	0x40022070	FULL	Master attributes 0
PERI_MS_PPU_FX97_MS_ATT1	0x40022074	FULL	Master attributes 1
PERI_MS_PPU_FX97_MS_ATT2	0x40022078	FULL	Master attributes 2
PERI_MS_PPU_FX97_MS_ATT3	0x4002207C	FULL	Master attributes 3

21.115 PPU_FX 98

Register Name	Address	Permission	Description
PERI_MS_PPU_FX98_SL_ADDR	0x40022080	FULL	Slave region, base address
PERI_MS_PPU_FX98_SL_SIZE	0x40022084	FULL	Slave region, size
PERI_MS_PPU_FX98_SL_ATT0	0x40022090	FULL	Slave attributes 0
PERI_MS_PPU_FX98_SL_ATT1	0x40022094	FULL	Slave attributes 1
PERI_MS_PPU_FX98_SL_ATT2	0x40022098	FULL	Slave attributes 2
PERI_MS_PPU_FX98_SL_ATT3	0x4002209C	FULL	Slave attributes 3
PERI_MS_PPU_FX98_MS_ADDR	0x400220A0	FULL	Master region, base address
PERI_MS_PPU_FX98_MS_SIZE	0x400220A4	FULL	Master region, size
PERI_MS_PPU_FX98_MS_ATT0	0x400220B0	FULL	Master attributes 0
PERI_MS_PPU_FX98_MS_ATT1	0x400220B4	FULL	Master attributes 1
PERI_MS_PPU_FX98_MS_ATT2	0x400220B8	FULL	Master attributes 2
PERI_MS_PPU_FX98_MS_ATT3	0x400220BC	FULL	Master attributes 3

21.116 PPU_FX 99

Register Name	Address	Permission	Description
PERI_MS_PPU_FX99_SL_ADDR	0x400220C0	FULL	Slave region, base address
PERI_MS_PPU_FX99_SL_SIZE	0x400220C4	FULL	Slave region, size
PERI_MS_PPU_FX99_SL_ATT0	0x400220D0	FULL	Slave attributes 0
PERI_MS_PPU_FX99_SL_ATT1	0x400220D4	FULL	Slave attributes 1
PERI_MS_PPU_FX99_SL_ATT2	0x400220D8	FULL	Slave attributes 2
PERI_MS_PPU_FX99_SL_ATT3	0x400220DC	FULL	Slave attributes 3
PERI_MS_PPU_FX99_MS_ADDR	0x400220E0	FULL	Master region, base address
PERI_MS_PPU_FX99_MS_SIZE	0x400220E4	FULL	Master region, size
PERI_MS_PPU_FX99_MS_ATT0	0x400220F0	FULL	Master attributes 0
PERI_MS_PPU_FX99_MS_ATT1	0x400220F4	FULL	Master attributes 1
PERI_MS_PPU_FX99_MS_ATT2	0x400220F8	FULL	Master attributes 2
PERI_MS_PPU_FX99_MS_ATT3	0x400220FC	FULL	Master attributes 3

21.117 PPU_FX 100

Register Name	Address	Permission	Description
PERI_MS_PPU_FX100_SL_ADDR	0x40022100	FULL	Slave region, base address
PERI_MS_PPU_FX100_SL_SIZE	0x40022104	FULL	Slave region, size
PERI_MS_PPU_FX100_SL_ATT0	0x40022110	FULL	Slave attributes 0
PERI_MS_PPU_FX100_SL_ATT1	0x40022114	FULL	Slave attributes 1
PERI_MS_PPU_FX100_SL_ATT2	0x40022118	FULL	Slave attributes 2
PERI_MS_PPU_FX100_SL_ATT3	0x4002211C	FULL	Slave attributes 3
PERI_MS_PPU_FX100_MS_ADDR	0x40022120	FULL	Master region, base address
PERI_MS_PPU_FX100_MS_SIZE	0x40022124	FULL	Master region, size
PERI_MS_PPU_FX100_MS_ATT0	0x40022130	FULL	Master attributes 0
PERI_MS_PPU_FX100_MS_ATT1	0x40022134	FULL	Master attributes 1
PERI_MS_PPU_FX100_MS_ATT2	0x40022138	FULL	Master attributes 2
PERI_MS_PPU_FX100_MS_ATT3	0x4002213C	FULL	Master attributes 3

21.118 PPU_FX 101

Register Name	Address	Permission	Description
PERI_MS_PPU_FX101_SL_ADDR	0x40022140	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX101_SL_SIZE	0x40022144	FULL	Slave region, size
PERI_MS_PPU_FX101_SL_ATT0	0x40022150	FULL	Slave attributes 0
PERI_MS_PPU_FX101_SL_ATT1	0x40022154	FULL	Slave attributes 1
PERI_MS_PPU_FX101_SL_ATT2	0x40022158	FULL	Slave attributes 2
PERI_MS_PPU_FX101_SL_ATT3	0x4002215C	FULL	Slave attributes 3
PERI_MS_PPU_FX101_MS_ADDR	0x40022160	FULL	Master region, base address
PERI_MS_PPU_FX101_MS_SIZE	0x40022164	FULL	Master region, size
PERI_MS_PPU_FX101_MS_ATT0	0x40022170	FULL	Master attributes 0
PERI_MS_PPU_FX101_MS_ATT1	0x40022174	FULL	Master attributes 1
PERI_MS_PPU_FX101_MS_ATT2	0x40022178	FULL	Master attributes 2
PERI_MS_PPU_FX101_MS_ATT3	0x4002217C	FULL	Master attributes 3

21.119 PPU_FX 102

Register Name	Address	Permission	Description
PERI_MS_PPU_FX102_SL_ADDR	0x40022180	FULL	Slave region, base address
PERI_MS_PPU_FX102_SL_SIZE	0x40022184	FULL	Slave region, size
PERI_MS_PPU_FX102_SL_ATT0	0x40022190	FULL	Slave attributes 0
PERI_MS_PPU_FX102_SL_ATT1	0x40022194	FULL	Slave attributes 1
PERI_MS_PPU_FX102_SL_ATT2	0x40022198	FULL	Slave attributes 2
PERI_MS_PPU_FX102_SL_ATT3	0x4002219C	FULL	Slave attributes 3
PERI_MS_PPU_FX102_MS_ADDR	0x400221A0	FULL	Master region, base address
PERI_MS_PPU_FX102_MS_SIZE	0x400221A4	FULL	Master region, size
PERI_MS_PPU_FX102_MS_ATT0	0x400221B0	FULL	Master attributes 0
PERI_MS_PPU_FX102_MS_ATT1	0x400221B4	FULL	Master attributes 1
PERI_MS_PPU_FX102_MS_ATT2	0x400221B8	FULL	Master attributes 2
PERI_MS_PPU_FX102_MS_ATT3	0x400221BC	FULL	Master attributes 3

21.120 PPU_FX 103

Register Name	Address	Permission	Description
PERI_MS_PPU_FX103_SL_ADDR	0x400221C0	FULL	Slave region, base address
PERI_MS_PPU_FX103_SL_SIZE	0x400221C4	FULL	Slave region, size
PERI_MS_PPU_FX103_SL_ATT0	0x400221D0	FULL	Slave attributes 0
PERI_MS_PPU_FX103_SL_ATT1	0x400221D4	FULL	Slave attributes 1
PERI_MS_PPU_FX103_SL_ATT2	0x400221D8	FULL	Slave attributes 2
PERI_MS_PPU_FX103_SL_ATT3	0x400221DC	FULL	Slave attributes 3
PERI_MS_PPU_FX103_MS_ADDR	0x400221E0	FULL	Master region, base address
PERI_MS_PPU_FX103_MS_SIZE	0x400221E4	FULL	Master region, size
PERI_MS_PPU_FX103_MS_ATT0	0x400221F0	FULL	Master attributes 0
PERI_MS_PPU_FX103_MS_ATT1	0x400221F4	FULL	Master attributes 1
PERI_MS_PPU_FX103_MS_ATT2	0x400221F8	FULL	Master attributes 2
PERI_MS_PPU_FX103_MS_ATT3	0x400221FC	FULL	Master attributes 3

21.121 PPU_FX 104

Register Name	Address	Permission	Description
PERI_MS_PPU_FX104_SL_ADDR	0x40022200	FULL	Slave region, base address
PERI_MS_PPU_FX104_SL_SIZE	0x40022204	FULL	Slave region, size
PERI_MS_PPU_FX104_SL_ATT0	0x40022210	FULL	Slave attributes 0
PERI_MS_PPU_FX104_SL_ATT1	0x40022214	FULL	Slave attributes 1
PERI_MS_PPU_FX104_SL_ATT2	0x40022218	FULL	Slave attributes 2
PERI_MS_PPU_FX104_SL_ATT3	0x4002221C	FULL	Slave attributes 3
PERI_MS_PPU_FX104_MS_ADDR	0x40022220	FULL	Master region, base address
PERI_MS_PPU_FX104_MS_SIZE	0x40022224	FULL	Master region, size
PERI_MS_PPU_FX104_MS_ATT0	0x40022230	FULL	Master attributes 0
PERI_MS_PPU_FX104_MS_ATT1	0x40022234	FULL	Master attributes 1
PERI_MS_PPU_FX104_MS_ATT2	0x40022238	FULL	Master attributes 2
PERI_MS_PPU_FX104_MS_ATT3	0x4002223C	FULL	Master attributes 3

21.122 PPU_FX 105

Register Name	Address	Permission	Description
PERI_MS_PPU_FX105_SL_ADDR	0x40022240	FULL	Slave region, base address
PERI_MS_PPU_FX105_SL_SIZE	0x40022244	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX105_SL_ATT0	0x40022250	FULL	Slave attributes 0
PERI_MS_PPU_FX105_SL_ATT1	0x40022254	FULL	Slave attributes 1
PERI_MS_PPU_FX105_SL_ATT2	0x40022258	FULL	Slave attributes 2
PERI_MS_PPU_FX105_SL_ATT3	0x4002225C	FULL	Slave attributes 3
PERI_MS_PPU_FX105_MS_ADDR	0x40022260	FULL	Master region, base address
PERI_MS_PPU_FX105_MS_SIZE	0x40022264	FULL	Master region, size
PERI_MS_PPU_FX105_MS_ATT0	0x40022270	FULL	Master attributes 0
PERI_MS_PPU_FX105_MS_ATT1	0x40022274	FULL	Master attributes 1
PERI_MS_PPU_FX105_MS_ATT2	0x40022278	FULL	Master attributes 2
PERI_MS_PPU_FX105_MS_ATT3	0x4002227C	FULL	Master attributes 3

21.123 PPU_FX 106

Register Name	Address	Permission	Description
PERI_MS_PPU_FX106_SL_ADDR	0x40022280	FULL	Slave region, base address
PERI_MS_PPU_FX106_SL_SIZE	0x40022284	FULL	Slave region, size
PERI_MS_PPU_FX106_SL_ATT0	0x40022290	FULL	Slave attributes 0
PERI_MS_PPU_FX106_SL_ATT1	0x40022294	FULL	Slave attributes 1
PERI_MS_PPU_FX106_SL_ATT2	0x40022298	FULL	Slave attributes 2
PERI_MS_PPU_FX106_SL_ATT3	0x4002229C	FULL	Slave attributes 3
PERI_MS_PPU_FX106_MS_ADDR	0x400222A0	FULL	Master region, base address
PERI_MS_PPU_FX106_MS_SIZE	0x400222A4	FULL	Master region, size
PERI_MS_PPU_FX106_MS_ATT0	0x400222B0	FULL	Master attributes 0
PERI_MS_PPU_FX106_MS_ATT1	0x400222B4	FULL	Master attributes 1
PERI_MS_PPU_FX106_MS_ATT2	0x400222B8	FULL	Master attributes 2
PERI_MS_PPU_FX106_MS_ATT3	0x400222BC	FULL	Master attributes 3

21.124 PPU_FX 107

Register Name	Address	Permission	Description
PERI_MS_PPU_FX107_SL_ADDR	0x400222C0	FULL	Slave region, base address
PERI_MS_PPU_FX107_SL_SIZE	0x400222C4	FULL	Slave region, size
PERI_MS_PPU_FX107_SL_ATT0	0x400222D0	FULL	Slave attributes 0
PERI_MS_PPU_FX107_SL_ATT1	0x400222D4	FULL	Slave attributes 1
PERI_MS_PPU_FX107_SL_ATT2	0x400222D8	FULL	Slave attributes 2
PERI_MS_PPU_FX107_SL_ATT3	0x400222DC	FULL	Slave attributes 3
PERI_MS_PPU_FX107_MS_ADDR	0x400222E0	FULL	Master region, base address
PERI_MS_PPU_FX107_MS_SIZE	0x400222E4	FULL	Master region, size
PERI_MS_PPU_FX107_MS_ATT0	0x400222F0	FULL	Master attributes 0
PERI_MS_PPU_FX107_MS_ATT1	0x400222F4	FULL	Master attributes 1
PERI_MS_PPU_FX107_MS_ATT2	0x400222F8	FULL	Master attributes 2
PERI_MS_PPU_FX107_MS_ATT3	0x400222FC	FULL	Master attributes 3

21.125 PPU_FX 108

Register Name	Address	Permission	Description
PERI_MS_PPU_FX108_SL_ADDR	0x40022300	FULL	Slave region, base address
PERI_MS_PPU_FX108_SL_SIZE	0x40022304	FULL	Slave region, size
PERI_MS_PPU_FX108_SL_ATT0	0x40022310	FULL	Slave attributes 0
PERI_MS_PPU_FX108_SL_ATT1	0x40022314	FULL	Slave attributes 1
PERI_MS_PPU_FX108_SL_ATT2	0x40022318	FULL	Slave attributes 2
PERI_MS_PPU_FX108_SL_ATT3	0x4002231C	FULL	Slave attributes 3
PERI_MS_PPU_FX108_MS_ADDR	0x40022320	FULL	Master region, base address
PERI_MS_PPU_FX108_MS_SIZE	0x40022324	FULL	Master region, size
PERI_MS_PPU_FX108_MS_ATT0	0x40022330	FULL	Master attributes 0
PERI_MS_PPU_FX108_MS_ATT1	0x40022334	FULL	Master attributes 1
PERI_MS_PPU_FX108_MS_ATT2	0x40022338	FULL	Master attributes 2
PERI_MS_PPU_FX108_MS_ATT3	0x4002233C	FULL	Master attributes 3

21.126 PPU_FX 109

Register Name	Address	Permission	Description
PERI_MS_PPU_FX109_SL_ADDR	0x40022340	FULL	Slave region, base address
PERI_MS_PPU_FX109_SL_SIZE	0x40022344	FULL	Slave region, size
PERI_MS_PPU_FX109_SL_ATT0	0x40022350	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX109_SL_ATT1	0x40022354	FULL	Slave attributes 1
PERI_MS_PPU_FX109_SL_ATT2	0x40022358	FULL	Slave attributes 2
PERI_MS_PPU_FX109_SL_ATT3	0x4002235C	FULL	Slave attributes 3
PERI_MS_PPU_FX109_MS_ADDR	0x40022360	FULL	Master region, base address
PERI_MS_PPU_FX109_MS_SIZE	0x40022364	FULL	Master region, size
PERI_MS_PPU_FX109_MS_ATT0	0x40022370	FULL	Master attributes 0
PERI_MS_PPU_FX109_MS_ATT1	0x40022374	FULL	Master attributes 1
PERI_MS_PPU_FX109_MS_ATT2	0x40022378	FULL	Master attributes 2
PERI_MS_PPU_FX109_MS_ATT3	0x4002237C	FULL	Master attributes 3

21.127 PPU_FX 110

Register Name	Address	Permission	Description
PERI_MS_PPU_FX110_SL_ADDR	0x40022380	FULL	Slave region, base address
PERI_MS_PPU_FX110_SL_SIZE	0x40022384	FULL	Slave region, size
PERI_MS_PPU_FX110_SL_ATT0	0x40022390	FULL	Slave attributes 0
PERI_MS_PPU_FX110_SL_ATT1	0x40022394	FULL	Slave attributes 1
PERI_MS_PPU_FX110_SL_ATT2	0x40022398	FULL	Slave attributes 2
PERI_MS_PPU_FX110_SL_ATT3	0x4002239C	FULL	Slave attributes 3
PERI_MS_PPU_FX110_MS_ADDR	0x400223A0	FULL	Master region, base address
PERI_MS_PPU_FX110_MS_SIZE	0x400223A4	FULL	Master region, size
PERI_MS_PPU_FX110_MS_ATT0	0x400223B0	FULL	Master attributes 0
PERI_MS_PPU_FX110_MS_ATT1	0x400223B4	FULL	Master attributes 1
PERI_MS_PPU_FX110_MS_ATT2	0x400223B8	FULL	Master attributes 2
PERI_MS_PPU_FX110_MS_ATT3	0x400223BC	FULL	Master attributes 3

21.128 PPU_FX 111

Register Name	Address	Permission	Description
PERI_MS_PPU_FX111_SL_ADDR	0x400223C0	FULL	Slave region, base address
PERI_MS_PPU_FX111_SL_SIZE	0x400223C4	FULL	Slave region, size
PERI_MS_PPU_FX111_SL_ATT0	0x400223D0	FULL	Slave attributes 0
PERI_MS_PPU_FX111_SL_ATT1	0x400223D4	FULL	Slave attributes 1
PERI_MS_PPU_FX111_SL_ATT2	0x400223D8	FULL	Slave attributes 2
PERI_MS_PPU_FX111_SL_ATT3	0x400223DC	FULL	Slave attributes 3
PERI_MS_PPU_FX111_MS_ADDR	0x400223E0	FULL	Master region, base address
PERI_MS_PPU_FX111_MS_SIZE	0x400223E4	FULL	Master region, size
PERI_MS_PPU_FX111_MS_ATT0	0x400223F0	FULL	Master attributes 0
PERI_MS_PPU_FX111_MS_ATT1	0x400223F4	FULL	Master attributes 1
PERI_MS_PPU_FX111_MS_ATT2	0x400223F8	FULL	Master attributes 2
PERI_MS_PPU_FX111_MS_ATT3	0x400223FC	FULL	Master attributes 3

21.129 PPU_FX 112

Register Name	Address	Permission	Description
PERI_MS_PPU_FX112_SL_ADDR	0x40022400	FULL	Slave region, base address
PERI_MS_PPU_FX112_SL_SIZE	0x40022404	FULL	Slave region, size
PERI_MS_PPU_FX112_SL_ATT0	0x40022410	FULL	Slave attributes 0
PERI_MS_PPU_FX112_SL_ATT1	0x40022414	FULL	Slave attributes 1
PERI_MS_PPU_FX112_SL_ATT2	0x40022418	FULL	Slave attributes 2
PERI_MS_PPU_FX112_SL_ATT3	0x4002241C	FULL	Slave attributes 3
PERI_MS_PPU_FX112_MS_ADDR	0x40022420	FULL	Master region, base address
PERI_MS_PPU_FX112_MS_SIZE	0x40022424	FULL	Master region, size
PERI_MS_PPU_FX112_MS_ATT0	0x40022430	FULL	Master attributes 0
PERI_MS_PPU_FX112_MS_ATT1	0x40022434	FULL	Master attributes 1
PERI_MS_PPU_FX112_MS_ATT2	0x40022438	FULL	Master attributes 2
PERI_MS_PPU_FX112_MS_ATT3	0x4002243C	FULL	Master attributes 3

21.130 PPU_FX 113

Register Name	Address	Permission	Description
PERI_MS_PPU_FX113_SL_ADDR	0x40022440	FULL	Slave region, base address
PERI_MS_PPU_FX113_SL_SIZE	0x40022444	FULL	Slave region, size
PERI_MS_PPU_FX113_SL_ATT0	0x40022450	FULL	Slave attributes 0
PERI_MS_PPU_FX113_SL_ATT1	0x40022454	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX113_SL_ATT2	0x40022458	FULL	Slave attributes 2
PERI_MS_PPU_FX113_SL_ATT3	0x4002245C	FULL	Slave attributes 3
PERI_MS_PPU_FX113_MS_ADDR	0x40022460	FULL	Master region, base address
PERI_MS_PPU_FX113_MS_SIZE	0x40022464	FULL	Master region, size
PERI_MS_PPU_FX113_MS_ATT0	0x40022470	FULL	Master attributes 0
PERI_MS_PPU_FX113_MS_ATT1	0x40022474	FULL	Master attributes 1
PERI_MS_PPU_FX113_MS_ATT2	0x40022478	FULL	Master attributes 2
PERI_MS_PPU_FX113_MS_ATT3	0x4002247C	FULL	Master attributes 3

21.131 PPU_FX 114

Register Name	Address	Permission	Description
PERI_MS_PPU_FX114_SL_ADDR	0x40022480	FULL	Slave region, base address
PERI_MS_PPU_FX114_SL_SIZE	0x40022484	FULL	Slave region, size
PERI_MS_PPU_FX114_SL_ATT0	0x40022490	FULL	Slave attributes 0
PERI_MS_PPU_FX114_SL_ATT1	0x40022494	FULL	Slave attributes 1
PERI_MS_PPU_FX114_SL_ATT2	0x40022498	FULL	Slave attributes 2
PERI_MS_PPU_FX114_SL_ATT3	0x4002249C	FULL	Slave attributes 3
PERI_MS_PPU_FX114_MS_ADDR	0x400224A0	FULL	Master region, base address
PERI_MS_PPU_FX114_MS_SIZE	0x400224A4	FULL	Master region, size
PERI_MS_PPU_FX114_MS_ATT0	0x400224B0	FULL	Master attributes 0
PERI_MS_PPU_FX114_MS_ATT1	0x400224B4	FULL	Master attributes 1
PERI_MS_PPU_FX114_MS_ATT2	0x400224B8	FULL	Master attributes 2
PERI_MS_PPU_FX114_MS_ATT3	0x400224BC	FULL	Master attributes 3

21.132 PPU_FX 115

Register Name	Address	Permission	Description
PERI_MS_PPU_FX115_SL_ADDR	0x400224C0	FULL	Slave region, base address
PERI_MS_PPU_FX115_SL_SIZE	0x400224C4	FULL	Slave region, size
PERI_MS_PPU_FX115_SL_ATT0	0x400224D0	FULL	Slave attributes 0
PERI_MS_PPU_FX115_SL_ATT1	0x400224D4	FULL	Slave attributes 1
PERI_MS_PPU_FX115_SL_ATT2	0x400224D8	FULL	Slave attributes 2
PERI_MS_PPU_FX115_SL_ATT3	0x400224DC	FULL	Slave attributes 3
PERI_MS_PPU_FX115_MS_ADDR	0x400224E0	FULL	Master region, base address
PERI_MS_PPU_FX115_MS_SIZE	0x400224E4	FULL	Master region, size
PERI_MS_PPU_FX115_MS_ATT0	0x400224F0	FULL	Master attributes 0
PERI_MS_PPU_FX115_MS_ATT1	0x400224F4	FULL	Master attributes 1
PERI_MS_PPU_FX115_MS_ATT2	0x400224F8	FULL	Master attributes 2
PERI_MS_PPU_FX115_MS_ATT3	0x400224FC	FULL	Master attributes 3

21.133 PPU_FX 116

Register Name	Address	Permission	Description
PERI_MS_PPU_FX116_SL_ADDR	0x40022500	FULL	Slave region, base address
PERI_MS_PPU_FX116_SL_SIZE	0x40022504	FULL	Slave region, size
PERI_MS_PPU_FX116_SL_ATT0	0x40022510	FULL	Slave attributes 0
PERI_MS_PPU_FX116_SL_ATT1	0x40022514	FULL	Slave attributes 1
PERI_MS_PPU_FX116_SL_ATT2	0x40022518	FULL	Slave attributes 2
PERI_MS_PPU_FX116_SL_ATT3	0x4002251C	FULL	Slave attributes 3
PERI_MS_PPU_FX116_MS_ADDR	0x40022520	FULL	Master region, base address
PERI_MS_PPU_FX116_MS_SIZE	0x40022524	FULL	Master region, size
PERI_MS_PPU_FX116_MS_ATT0	0x40022530	FULL	Master attributes 0
PERI_MS_PPU_FX116_MS_ATT1	0x40022534	FULL	Master attributes 1
PERI_MS_PPU_FX116_MS_ATT2	0x40022538	FULL	Master attributes 2
PERI_MS_PPU_FX116_MS_ATT3	0x4002253C	FULL	Master attributes 3

21.134 PPU_FX 117

Register Name	Address	Permission	Description
PERI_MS_PPU_FX117_SL_ADDR	0x40022540	FULL	Slave region, base address
PERI_MS_PPU_FX117_SL_SIZE	0x40022544	FULL	Slave region, size
PERI_MS_PPU_FX117_SL_ATT0	0x40022550	FULL	Slave attributes 0
PERI_MS_PPU_FX117_SL_ATT1	0x40022554	FULL	Slave attributes 1
PERI_MS_PPU_FX117_SL_ATT2	0x40022558	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX117_SL_ATT3	0x4002255C	FULL	Slave attributes 3
PERI_MS_PPU_FX117_MS_ADDR	0x40022560	FULL	Master region, base address
PERI_MS_PPU_FX117_MS_SIZE	0x40022564	FULL	Master region, size
PERI_MS_PPU_FX117_MS_ATT0	0x40022570	FULL	Master attributes 0
PERI_MS_PPU_FX117_MS_ATT1	0x40022574	FULL	Master attributes 1
PERI_MS_PPU_FX117_MS_ATT2	0x40022578	FULL	Master attributes 2
PERI_MS_PPU_FX117_MS_ATT3	0x4002257C	FULL	Master attributes 3

21.135 PPU_FX 118

Register Name	Address	Permission	Description
PERI_MS_PPU_FX118_SL_ADDR	0x40022580	FULL	Slave region, base address
PERI_MS_PPU_FX118_SL_SIZE	0x40022584	FULL	Slave region, size
PERI_MS_PPU_FX118_SL_ATT0	0x40022590	FULL	Slave attributes 0
PERI_MS_PPU_FX118_SL_ATT1	0x40022594	FULL	Slave attributes 1
PERI_MS_PPU_FX118_SL_ATT2	0x40022598	FULL	Slave attributes 2
PERI_MS_PPU_FX118_SL_ATT3	0x4002259C	FULL	Slave attributes 3
PERI_MS_PPU_FX118_MS_ADDR	0x400225A0	FULL	Master region, base address
PERI_MS_PPU_FX118_MS_SIZE	0x400225A4	FULL	Master region, size
PERI_MS_PPU_FX118_MS_ATT0	0x400225B0	FULL	Master attributes 0
PERI_MS_PPU_FX118_MS_ATT1	0x400225B4	FULL	Master attributes 1
PERI_MS_PPU_FX118_MS_ATT2	0x400225B8	FULL	Master attributes 2
PERI_MS_PPU_FX118_MS_ATT3	0x400225BC	FULL	Master attributes 3

21.136 PPU_FX 119

Register Name	Address	Permission	Description
PERI_MS_PPU_FX119_SL_ADDR	0x400225C0	FULL	Slave region, base address
PERI_MS_PPU_FX119_SL_SIZE	0x400225C4	FULL	Slave region, size
PERI_MS_PPU_FX119_SL_ATT0	0x400225D0	FULL	Slave attributes 0
PERI_MS_PPU_FX119_SL_ATT1	0x400225D4	FULL	Slave attributes 1
PERI_MS_PPU_FX119_SL_ATT2	0x400225D8	FULL	Slave attributes 2
PERI_MS_PPU_FX119_SL_ATT3	0x400225DC	FULL	Slave attributes 3
PERI_MS_PPU_FX119_MS_ADDR	0x400225E0	FULL	Master region, base address
PERI_MS_PPU_FX119_MS_SIZE	0x400225E4	FULL	Master region, size
PERI_MS_PPU_FX119_MS_ATT0	0x400225F0	FULL	Master attributes 0
PERI_MS_PPU_FX119_MS_ATT1	0x400225F4	FULL	Master attributes 1
PERI_MS_PPU_FX119_MS_ATT2	0x400225F8	FULL	Master attributes 2
PERI_MS_PPU_FX119_MS_ATT3	0x400225FC	FULL	Master attributes 3

21.137 PPU_FX 120

Register Name	Address	Permission	Description
PERI_MS_PPU_FX120_SL_ADDR	0x40022600	FULL	Slave region, base address
PERI_MS_PPU_FX120_SL_SIZE	0x40022604	FULL	Slave region, size
PERI_MS_PPU_FX120_SL_ATT0	0x40022610	FULL	Slave attributes 0
PERI_MS_PPU_FX120_SL_ATT1	0x40022614	FULL	Slave attributes 1
PERI_MS_PPU_FX120_SL_ATT2	0x40022618	FULL	Slave attributes 2
PERI_MS_PPU_FX120_SL_ATT3	0x4002261C	FULL	Slave attributes 3
PERI_MS_PPU_FX120_MS_ADDR	0x40022620	FULL	Master region, base address
PERI_MS_PPU_FX120_MS_SIZE	0x40022624	FULL	Master region, size
PERI_MS_PPU_FX120_MS_ATT0	0x40022630	FULL	Master attributes 0
PERI_MS_PPU_FX120_MS_ATT1	0x40022634	FULL	Master attributes 1
PERI_MS_PPU_FX120_MS_ATT2	0x40022638	FULL	Master attributes 2
PERI_MS_PPU_FX120_MS_ATT3	0x4002263C	FULL	Master attributes 3

21.138 PPU_FX 121

Register Name	Address	Permission	Description
PERI_MS_PPU_FX121_SL_ADDR	0x40022640	FULL	Slave region, base address
PERI_MS_PPU_FX121_SL_SIZE	0x40022644	FULL	Slave region, size
PERI_MS_PPU_FX121_SL_ATT0	0x40022650	FULL	Slave attributes 0
PERI_MS_PPU_FX121_SL_ATT1	0x40022654	FULL	Slave attributes 1
PERI_MS_PPU_FX121_SL_ATT2	0x40022658	FULL	Slave attributes 2
PERI_MS_PPU_FX121_SL_ATT3	0x4002265C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX121_MS_ADDR	0x40022660	FULL	Master region, base address
PERI_MS_PPU_FX121_MS_SIZE	0x40022664	FULL	Master region, size
PERI_MS_PPU_FX121_MS_ATT0	0x40022670	FULL	Master attributes 0
PERI_MS_PPU_FX121_MS_ATT1	0x40022674	FULL	Master attributes 1
PERI_MS_PPU_FX121_MS_ATT2	0x40022678	FULL	Master attributes 2
PERI_MS_PPU_FX121_MS_ATT3	0x4002267C	FULL	Master attributes 3

21.139 PPU_FX 122

Register Name	Address	Permission	Description
PERI_MS_PPU_FX122_SL_ADDR	0x40022680	FULL	Slave region, base address
PERI_MS_PPU_FX122_SL_SIZE	0x40022684	FULL	Slave region, size
PERI_MS_PPU_FX122_SL_ATT0	0x40022690	FULL	Slave attributes 0
PERI_MS_PPU_FX122_SL_ATT1	0x40022694	FULL	Slave attributes 1
PERI_MS_PPU_FX122_SL_ATT2	0x40022698	FULL	Slave attributes 2
PERI_MS_PPU_FX122_SL_ATT3	0x4002269C	FULL	Slave attributes 3
PERI_MS_PPU_FX122_MS_ADDR	0x400226A0	FULL	Master region, base address
PERI_MS_PPU_FX122_MS_SIZE	0x400226A4	FULL	Master region, size
PERI_MS_PPU_FX122_MS_ATT0	0x400226B0	FULL	Master attributes 0
PERI_MS_PPU_FX122_MS_ATT1	0x400226B4	FULL	Master attributes 1
PERI_MS_PPU_FX122_MS_ATT2	0x400226B8	FULL	Master attributes 2
PERI_MS_PPU_FX122_MS_ATT3	0x400226BC	FULL	Master attributes 3

21.140 PPU_FX 123

Register Name	Address	Permission	Description
PERI_MS_PPU_FX123_SL_ADDR	0x400226C0	FULL	Slave region, base address
PERI_MS_PPU_FX123_SL_SIZE	0x400226C4	FULL	Slave region, size
PERI_MS_PPU_FX123_SL_ATT0	0x400226D0	FULL	Slave attributes 0
PERI_MS_PPU_FX123_SL_ATT1	0x400226D4	FULL	Slave attributes 1
PERI_MS_PPU_FX123_SL_ATT2	0x400226D8	FULL	Slave attributes 2
PERI_MS_PPU_FX123_SL_ATT3	0x400226DC	FULL	Slave attributes 3
PERI_MS_PPU_FX123_MS_ADDR	0x400226E0	FULL	Master region, base address
PERI_MS_PPU_FX123_MS_SIZE	0x400226E4	FULL	Master region, size
PERI_MS_PPU_FX123_MS_ATT0	0x400226F0	FULL	Master attributes 0
PERI_MS_PPU_FX123_MS_ATT1	0x400226F4	FULL	Master attributes 1
PERI_MS_PPU_FX123_MS_ATT2	0x400226F8	FULL	Master attributes 2
PERI_MS_PPU_FX123_MS_ATT3	0x400226FC	FULL	Master attributes 3

21.141 PPU_FX 124

Register Name	Address	Permission	Description
PERI_MS_PPU_FX124_SL_ADDR	0x40022700	FULL	Slave region, base address
PERI_MS_PPU_FX124_SL_SIZE	0x40022704	FULL	Slave region, size
PERI_MS_PPU_FX124_SL_ATT0	0x40022710	FULL	Slave attributes 0
PERI_MS_PPU_FX124_SL_ATT1	0x40022714	FULL	Slave attributes 1
PERI_MS_PPU_FX124_SL_ATT2	0x40022718	FULL	Slave attributes 2
PERI_MS_PPU_FX124_SL_ATT3	0x4002271C	FULL	Slave attributes 3
PERI_MS_PPU_FX124_MS_ADDR	0x40022720	FULL	Master region, base address
PERI_MS_PPU_FX124_MS_SIZE	0x40022724	FULL	Master region, size
PERI_MS_PPU_FX124_MS_ATT0	0x40022730	FULL	Master attributes 0
PERI_MS_PPU_FX124_MS_ATT1	0x40022734	FULL	Master attributes 1
PERI_MS_PPU_FX124_MS_ATT2	0x40022738	FULL	Master attributes 2
PERI_MS_PPU_FX124_MS_ATT3	0x4002273C	FULL	Master attributes 3

21.142 PPU_FX 125

Register Name	Address	Permission	Description
PERI_MS_PPU_FX125_SL_ADDR	0x40022740	FULL	Slave region, base address
PERI_MS_PPU_FX125_SL_SIZE	0x40022744	FULL	Slave region, size
PERI_MS_PPU_FX125_SL_ATT0	0x40022750	FULL	Slave attributes 0
PERI_MS_PPU_FX125_SL_ATT1	0x40022754	FULL	Slave attributes 1
PERI_MS_PPU_FX125_SL_ATT2	0x40022758	FULL	Slave attributes 2
PERI_MS_PPU_FX125_SL_ATT3	0x4002275C	FULL	Slave attributes 3
PERI_MS_PPU_FX125_MS_ADDR	0x40022760	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX125_MS_SIZE	0x40022764	FULL	Master region, size
PERI_MS_PPU_FX125_MS_ATT0	0x40022770	FULL	Master attributes 0
PERI_MS_PPU_FX125_MS_ATT1	0x40022774	FULL	Master attributes 1
PERI_MS_PPU_FX125_MS_ATT2	0x40022778	FULL	Master attributes 2
PERI_MS_PPU_FX125_MS_ATT3	0x4002277C	FULL	Master attributes 3

21.143 PPU_FX 126

Register Name	Address	Permission	Description
PERI_MS_PPU_FX126_SL_ADDR	0x40022780	FULL	Slave region, base address
PERI_MS_PPU_FX126_SL_SIZE	0x40022784	FULL	Slave region, size
PERI_MS_PPU_FX126_SL_ATT0	0x40022790	FULL	Slave attributes 0
PERI_MS_PPU_FX126_SL_ATT1	0x40022794	FULL	Slave attributes 1
PERI_MS_PPU_FX126_SL_ATT2	0x40022798	FULL	Slave attributes 2
PERI_MS_PPU_FX126_SL_ATT3	0x4002279C	FULL	Slave attributes 3
PERI_MS_PPU_FX126_MS_ADDR	0x400227A0	FULL	Master region, base address
PERI_MS_PPU_FX126_MS_SIZE	0x400227A4	FULL	Master region, size
PERI_MS_PPU_FX126_MS_ATT0	0x400227B0	FULL	Master attributes 0
PERI_MS_PPU_FX126_MS_ATT1	0x400227B4	FULL	Master attributes 1
PERI_MS_PPU_FX126_MS_ATT2	0x400227B8	FULL	Master attributes 2
PERI_MS_PPU_FX126_MS_ATT3	0x400227BC	FULL	Master attributes 3

21.144 PPU_FX 127

Register Name	Address	Permission	Description
PERI_MS_PPU_FX127_SL_ADDR	0x400227C0	FULL	Slave region, base address
PERI_MS_PPU_FX127_SL_SIZE	0x400227C4	FULL	Slave region, size
PERI_MS_PPU_FX127_SL_ATT0	0x400227D0	FULL	Slave attributes 0
PERI_MS_PPU_FX127_SL_ATT1	0x400227D4	FULL	Slave attributes 1
PERI_MS_PPU_FX127_SL_ATT2	0x400227D8	FULL	Slave attributes 2
PERI_MS_PPU_FX127_SL_ATT3	0x400227DC	FULL	Slave attributes 3
PERI_MS_PPU_FX127_MS_ADDR	0x400227E0	FULL	Master region, base address
PERI_MS_PPU_FX127_MS_SIZE	0x400227E4	FULL	Master region, size
PERI_MS_PPU_FX127_MS_ATT0	0x400227F0	FULL	Master attributes 0
PERI_MS_PPU_FX127_MS_ATT1	0x400227F4	FULL	Master attributes 1
PERI_MS_PPU_FX127_MS_ATT2	0x400227F8	FULL	Master attributes 2
PERI_MS_PPU_FX127_MS_ATT3	0x400227FC	FULL	Master attributes 3

21.145 PPU_FX 128

Register Name	Address	Permission	Description
PERI_MS_PPU_FX128_SL_ADDR	0x40022800	FULL	Slave region, base address
PERI_MS_PPU_FX128_SL_SIZE	0x40022804	FULL	Slave region, size
PERI_MS_PPU_FX128_SL_ATT0	0x40022810	FULL	Slave attributes 0
PERI_MS_PPU_FX128_SL_ATT1	0x40022814	FULL	Slave attributes 1
PERI_MS_PPU_FX128_SL_ATT2	0x40022818	FULL	Slave attributes 2
PERI_MS_PPU_FX128_SL_ATT3	0x4002281C	FULL	Slave attributes 3
PERI_MS_PPU_FX128_MS_ADDR	0x40022820	FULL	Master region, base address
PERI_MS_PPU_FX128_MS_SIZE	0x40022824	FULL	Master region, size
PERI_MS_PPU_FX128_MS_ATT0	0x40022830	FULL	Master attributes 0
PERI_MS_PPU_FX128_MS_ATT1	0x40022834	FULL	Master attributes 1
PERI_MS_PPU_FX128_MS_ATT2	0x40022838	FULL	Master attributes 2
PERI_MS_PPU_FX128_MS_ATT3	0x4002283C	FULL	Master attributes 3

21.146 PPU_FX 129

Register Name	Address	Permission	Description
PERI_MS_PPU_FX129_SL_ADDR	0x40022840	FULL	Slave region, base address
PERI_MS_PPU_FX129_SL_SIZE	0x40022844	FULL	Slave region, size
PERI_MS_PPU_FX129_SL_ATT0	0x40022850	FULL	Slave attributes 0
PERI_MS_PPU_FX129_SL_ATT1	0x40022854	FULL	Slave attributes 1
PERI_MS_PPU_FX129_SL_ATT2	0x40022858	FULL	Slave attributes 2
PERI_MS_PPU_FX129_SL_ATT3	0x4002285C	FULL	Slave attributes 3
PERI_MS_PPU_FX129_MS_ADDR	0x40022860	FULL	Master region, base address
PERI_MS_PPU_FX129_MS_SIZE	0x40022864	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX129_MS_ATT0	0x40022870	FULL	Master attributes 0
PERI_MS_PPU_FX129_MS_ATT1	0x40022874	FULL	Master attributes 1
PERI_MS_PPU_FX129_MS_ATT2	0x40022878	FULL	Master attributes 2
PERI_MS_PPU_FX129_MS_ATT3	0x4002287C	FULL	Master attributes 3

21.147 PPU_FX 130

Register Name	Address	Permission	Description
PERI_MS_PPU_FX130_SL_ADDR	0x40022880	FULL	Slave region, base address
PERI_MS_PPU_FX130_SL_SIZE	0x40022884	FULL	Slave region, size
PERI_MS_PPU_FX130_SL_ATT0	0x40022890	FULL	Slave attributes 0
PERI_MS_PPU_FX130_SL_ATT1	0x40022894	FULL	Slave attributes 1
PERI_MS_PPU_FX130_SL_ATT2	0x40022898	FULL	Slave attributes 2
PERI_MS_PPU_FX130_SL_ATT3	0x4002289C	FULL	Slave attributes 3
PERI_MS_PPU_FX130_MS_ADDR	0x400228A0	FULL	Master region, base address
PERI_MS_PPU_FX130_MS_SIZE	0x400228A4	FULL	Master region, size
PERI_MS_PPU_FX130_MS_ATT0	0x400228B0	FULL	Master attributes 0
PERI_MS_PPU_FX130_MS_ATT1	0x400228B4	FULL	Master attributes 1
PERI_MS_PPU_FX130_MS_ATT2	0x400228B8	FULL	Master attributes 2
PERI_MS_PPU_FX130_MS_ATT3	0x400228BC	FULL	Master attributes 3

21.148 PPU_FX 131

Register Name	Address	Permission	Description
PERI_MS_PPU_FX131_SL_ADDR	0x400228C0	FULL	Slave region, base address
PERI_MS_PPU_FX131_SL_SIZE	0x400228C4	FULL	Slave region, size
PERI_MS_PPU_FX131_SL_ATT0	0x400228D0	FULL	Slave attributes 0
PERI_MS_PPU_FX131_SL_ATT1	0x400228D4	FULL	Slave attributes 1
PERI_MS_PPU_FX131_SL_ATT2	0x400228D8	FULL	Slave attributes 2
PERI_MS_PPU_FX131_SL_ATT3	0x400228DC	FULL	Slave attributes 3
PERI_MS_PPU_FX131_MS_ADDR	0x400228E0	FULL	Master region, base address
PERI_MS_PPU_FX131_MS_SIZE	0x400228E4	FULL	Master region, size
PERI_MS_PPU_FX131_MS_ATT0	0x400228F0	FULL	Master attributes 0
PERI_MS_PPU_FX131_MS_ATT1	0x400228F4	FULL	Master attributes 1
PERI_MS_PPU_FX131_MS_ATT2	0x400228F8	FULL	Master attributes 2
PERI_MS_PPU_FX131_MS_ATT3	0x400228FC	FULL	Master attributes 3

21.149 PPU_FX 132

Register Name	Address	Permission	Description
PERI_MS_PPU_FX132_SL_ADDR	0x40022900	FULL	Slave region, base address
PERI_MS_PPU_FX132_SL_SIZE	0x40022904	FULL	Slave region, size
PERI_MS_PPU_FX132_SL_ATT0	0x40022910	FULL	Slave attributes 0
PERI_MS_PPU_FX132_SL_ATT1	0x40022914	FULL	Slave attributes 1
PERI_MS_PPU_FX132_SL_ATT2	0x40022918	FULL	Slave attributes 2
PERI_MS_PPU_FX132_SL_ATT3	0x4002291C	FULL	Slave attributes 3
PERI_MS_PPU_FX132_MS_ADDR	0x40022920	FULL	Master region, base address
PERI_MS_PPU_FX132_MS_SIZE	0x40022924	FULL	Master region, size
PERI_MS_PPU_FX132_MS_ATT0	0x40022930	FULL	Master attributes 0
PERI_MS_PPU_FX132_MS_ATT1	0x40022934	FULL	Master attributes 1
PERI_MS_PPU_FX132_MS_ATT2	0x40022938	FULL	Master attributes 2
PERI_MS_PPU_FX132_MS_ATT3	0x4002293C	FULL	Master attributes 3

21.150 PPU_FX 133

Register Name	Address	Permission	Description
PERI_MS_PPU_FX133_SL_ADDR	0x40022940	FULL	Slave region, base address
PERI_MS_PPU_FX133_SL_SIZE	0x40022944	FULL	Slave region, size
PERI_MS_PPU_FX133_SL_ATT0	0x40022950	FULL	Slave attributes 0
PERI_MS_PPU_FX133_SL_ATT1	0x40022954	FULL	Slave attributes 1
PERI_MS_PPU_FX133_SL_ATT2	0x40022958	FULL	Slave attributes 2
PERI_MS_PPU_FX133_SL_ATT3	0x4002295C	FULL	Slave attributes 3
PERI_MS_PPU_FX133_MS_ADDR	0x40022960	FULL	Master region, base address
PERI_MS_PPU_FX133_MS_SIZE	0x40022964	FULL	Master region, size
PERI_MS_PPU_FX133_MS_ATT0	0x40022970	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX133_MS_ATT1	0x40022974	FULL	Master attributes 1
PERI_MS_PPU_FX133_MS_ATT2	0x40022978	FULL	Master attributes 2
PERI_MS_PPU_FX133_MS_ATT3	0x4002297C	FULL	Master attributes 3

21.151 PPU_FX 134

Register Name	Address	Permission	Description
PERI_MS_PPU_FX134_SL_ADDR	0x40022980	FULL	Slave region, base address
PERI_MS_PPU_FX134_SL_SIZE	0x40022984	FULL	Slave region, size
PERI_MS_PPU_FX134_SL_ATT0	0x40022990	FULL	Slave attributes 0
PERI_MS_PPU_FX134_SL_ATT1	0x40022994	FULL	Slave attributes 1
PERI_MS_PPU_FX134_SL_ATT2	0x40022998	FULL	Slave attributes 2
PERI_MS_PPU_FX134_SL_ATT3	0x4002299C	FULL	Slave attributes 3
PERI_MS_PPU_FX134_MS_ADDR	0x400229A0	FULL	Master region, base address
PERI_MS_PPU_FX134_MS_SIZE	0x400229A4	FULL	Master region, size
PERI_MS_PPU_FX134_MS_ATT0	0x400229B0	FULL	Master attributes 0
PERI_MS_PPU_FX134_MS_ATT1	0x400229B4	FULL	Master attributes 1
PERI_MS_PPU_FX134_MS_ATT2	0x400229B8	FULL	Master attributes 2
PERI_MS_PPU_FX134_MS_ATT3	0x400229BC	FULL	Master attributes 3

21.152 PPU_FX 135

Register Name	Address	Permission	Description
PERI_MS_PPU_FX135_SL_ADDR	0x400229C0	FULL	Slave region, base address
PERI_MS_PPU_FX135_SL_SIZE	0x400229C4	FULL	Slave region, size
PERI_MS_PPU_FX135_SL_ATT0	0x400229D0	FULL	Slave attributes 0
PERI_MS_PPU_FX135_SL_ATT1	0x400229D4	FULL	Slave attributes 1
PERI_MS_PPU_FX135_SL_ATT2	0x400229D8	FULL	Slave attributes 2
PERI_MS_PPU_FX135_SL_ATT3	0x400229DC	FULL	Slave attributes 3
PERI_MS_PPU_FX135_MS_ADDR	0x400229E0	FULL	Master region, base address
PERI_MS_PPU_FX135_MS_SIZE	0x400229E4	FULL	Master region, size
PERI_MS_PPU_FX135_MS_ATT0	0x400229F0	FULL	Master attributes 0
PERI_MS_PPU_FX135_MS_ATT1	0x400229F4	FULL	Master attributes 1
PERI_MS_PPU_FX135_MS_ATT2	0x400229F8	FULL	Master attributes 2
PERI_MS_PPU_FX135_MS_ATT3	0x400229FC	FULL	Master attributes 3

21.153 PPU_FX 136

Register Name	Address	Permission	Description
PERI_MS_PPU_FX136_SL_ADDR	0x40022A00	FULL	Slave region, base address
PERI_MS_PPU_FX136_SL_SIZE	0x40022A04	FULL	Slave region, size
PERI_MS_PPU_FX136_SL_ATT0	0x40022A10	FULL	Slave attributes 0
PERI_MS_PPU_FX136_SL_ATT1	0x40022A14	FULL	Slave attributes 1
PERI_MS_PPU_FX136_SL_ATT2	0x40022A18	FULL	Slave attributes 2
PERI_MS_PPU_FX136_SL_ATT3	0x40022A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX136_MS_ADDR	0x40022A20	FULL	Master region, base address
PERI_MS_PPU_FX136_MS_SIZE	0x40022A24	FULL	Master region, size
PERI_MS_PPU_FX136_MS_ATT0	0x40022A30	FULL	Master attributes 0
PERI_MS_PPU_FX136_MS_ATT1	0x40022A34	FULL	Master attributes 1
PERI_MS_PPU_FX136_MS_ATT2	0x40022A38	FULL	Master attributes 2
PERI_MS_PPU_FX136_MS_ATT3	0x40022A3C	FULL	Master attributes 3

21.154 PPU_FX 137

Register Name	Address	Permission	Description
PERI_MS_PPU_FX137_SL_ADDR	0x40022A40	FULL	Slave region, base address
PERI_MS_PPU_FX137_SL_SIZE	0x40022A44	FULL	Slave region, size
PERI_MS_PPU_FX137_SL_ATT0	0x40022A50	FULL	Slave attributes 0
PERI_MS_PPU_FX137_SL_ATT1	0x40022A54	FULL	Slave attributes 1
PERI_MS_PPU_FX137_SL_ATT2	0x40022A58	FULL	Slave attributes 2
PERI_MS_PPU_FX137_SL_ATT3	0x40022A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX137_MS_ADDR	0x40022A60	FULL	Master region, base address
PERI_MS_PPU_FX137_MS_SIZE	0x40022A64	FULL	Master region, size
PERI_MS_PPU_FX137_MS_ATT0	0x40022A70	FULL	Master attributes 0
PERI_MS_PPU_FX137_MS_ATT1	0x40022A74	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX137_MS_ATT2	0x40022A78	FULL	Master attributes 2
PERI_MS_PPU_FX137_MS_ATT3	0x40022A7C	FULL	Master attributes 3

21.155 PPU_FX 138

Register Name	Address	Permission	Description
PERI_MS_PPU_FX138_SL_ADDR	0x40022A80	FULL	Slave region, base address
PERI_MS_PPU_FX138_SL_SIZE	0x40022A84	FULL	Slave region, size
PERI_MS_PPU_FX138_SL_ATT0	0x40022A90	FULL	Slave attributes 0
PERI_MS_PPU_FX138_SL_ATT1	0x40022A94	FULL	Slave attributes 1
PERI_MS_PPU_FX138_SL_ATT2	0x40022A98	FULL	Slave attributes 2
PERI_MS_PPU_FX138_SL_ATT3	0x40022A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX138_MS_ADDR	0x40022AA0	FULL	Master region, base address
PERI_MS_PPU_FX138_MS_SIZE	0x40022AA4	FULL	Master region, size
PERI_MS_PPU_FX138_MS_ATT0	0x40022AB0	FULL	Master attributes 0
PERI_MS_PPU_FX138_MS_ATT1	0x40022AB4	FULL	Master attributes 1
PERI_MS_PPU_FX138_MS_ATT2	0x40022AB8	FULL	Master attributes 2
PERI_MS_PPU_FX138_MS_ATT3	0x40022ABC	FULL	Master attributes 3

21.156 PPU_FX 139

Register Name	Address	Permission	Description
PERI_MS_PPU_FX139_SL_ADDR	0x40022AC0	FULL	Slave region, base address
PERI_MS_PPU_FX139_SL_SIZE	0x40022AC4	FULL	Slave region, size
PERI_MS_PPU_FX139_SL_ATT0	0x40022AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX139_SL_ATT1	0x40022AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX139_SL_ATT2	0x40022AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX139_SL_ATT3	0x40022ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX139_MS_ADDR	0x40022AE0	FULL	Master region, base address
PERI_MS_PPU_FX139_MS_SIZE	0x40022AE4	FULL	Master region, size
PERI_MS_PPU_FX139_MS_ATT0	0x40022AF0	FULL	Master attributes 0
PERI_MS_PPU_FX139_MS_ATT1	0x40022AF4	FULL	Master attributes 1
PERI_MS_PPU_FX139_MS_ATT2	0x40022AF8	FULL	Master attributes 2
PERI_MS_PPU_FX139_MS_ATT3	0x40022AFC	FULL	Master attributes 3

21.157 PPU_FX 140

Register Name	Address	Permission	Description
PERI_MS_PPU_FX140_SL_ADDR	0x40022B00	FULL	Slave region, base address
PERI_MS_PPU_FX140_SL_SIZE	0x40022B04	FULL	Slave region, size
PERI_MS_PPU_FX140_SL_ATT0	0x40022B10	FULL	Slave attributes 0
PERI_MS_PPU_FX140_SL_ATT1	0x40022B14	FULL	Slave attributes 1
PERI_MS_PPU_FX140_SL_ATT2	0x40022B18	FULL	Slave attributes 2
PERI_MS_PPU_FX140_SL_ATT3	0x40022B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX140_MS_ADDR	0x40022B20	FULL	Master region, base address
PERI_MS_PPU_FX140_MS_SIZE	0x40022B24	FULL	Master region, size
PERI_MS_PPU_FX140_MS_ATT0	0x40022B30	FULL	Master attributes 0
PERI_MS_PPU_FX140_MS_ATT1	0x40022B34	FULL	Master attributes 1
PERI_MS_PPU_FX140_MS_ATT2	0x40022B38	FULL	Master attributes 2
PERI_MS_PPU_FX140_MS_ATT3	0x40022B3C	FULL	Master attributes 3

21.158 PPU_FX 141

Register Name	Address	Permission	Description
PERI_MS_PPU_FX141_SL_ADDR	0x40022B40	FULL	Slave region, base address
PERI_MS_PPU_FX141_SL_SIZE	0x40022B44	FULL	Slave region, size
PERI_MS_PPU_FX141_SL_ATT0	0x40022B50	FULL	Slave attributes 0
PERI_MS_PPU_FX141_SL_ATT1	0x40022B54	FULL	Slave attributes 1
PERI_MS_PPU_FX141_SL_ATT2	0x40022B58	FULL	Slave attributes 2
PERI_MS_PPU_FX141_SL_ATT3	0x40022B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX141_MS_ADDR	0x40022B60	FULL	Master region, base address
PERI_MS_PPU_FX141_MS_SIZE	0x40022B64	FULL	Master region, size
PERI_MS_PPU_FX141_MS_ATT0	0x40022B70	FULL	Master attributes 0
PERI_MS_PPU_FX141_MS_ATT1	0x40022B74	FULL	Master attributes 1
PERI_MS_PPU_FX141_MS_ATT2	0x40022B78	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX141_MS_ATT3	0x40022B7C	FULL	Master attributes 3

21.159 PPU_FX 142

Register Name	Address	Permission	Description
PERI_MS_PPU_FX142_SL_ADDR	0x40022B80	FULL	Slave region, base address
PERI_MS_PPU_FX142_SL_SIZE	0x40022B84	FULL	Slave region, size
PERI_MS_PPU_FX142_SL_ATT0	0x40022B90	FULL	Slave attributes 0
PERI_MS_PPU_FX142_SL_ATT1	0x40022B94	FULL	Slave attributes 1
PERI_MS_PPU_FX142_SL_ATT2	0x40022B98	FULL	Slave attributes 2
PERI_MS_PPU_FX142_SL_ATT3	0x40022B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX142_MS_ADDR	0x40022BA0	FULL	Master region, base address
PERI_MS_PPU_FX142_MS_SIZE	0x40022BA4	FULL	Master region, size
PERI_MS_PPU_FX142_MS_ATT0	0x40022BB0	FULL	Master attributes 0
PERI_MS_PPU_FX142_MS_ATT1	0x40022BB4	FULL	Master attributes 1
PERI_MS_PPU_FX142_MS_ATT2	0x40022BB8	FULL	Master attributes 2
PERI_MS_PPU_FX142_MS_ATT3	0x40022BBC	FULL	Master attributes 3

21.160 PPU_FX 143

Register Name	Address	Permission	Description
PERI_MS_PPU_FX143_SL_ADDR	0x40022BC0	FULL	Slave region, base address
PERI_MS_PPU_FX143_SL_SIZE	0x40022BC4	FULL	Slave region, size
PERI_MS_PPU_FX143_SL_ATT0	0x40022BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX143_SL_ATT1	0x40022BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX143_SL_ATT2	0x40022BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX143_SL_ATT3	0x40022BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX143_MS_ADDR	0x40022BE0	FULL	Master region, base address
PERI_MS_PPU_FX143_MS_SIZE	0x40022BE4	FULL	Master region, size
PERI_MS_PPU_FX143_MS_ATT0	0x40022BF0	FULL	Master attributes 0
PERI_MS_PPU_FX143_MS_ATT1	0x40022BF4	FULL	Master attributes 1
PERI_MS_PPU_FX143_MS_ATT2	0x40022BF8	FULL	Master attributes 2
PERI_MS_PPU_FX143_MS_ATT3	0x40022BFC	FULL	Master attributes 3

21.161 PPU_FX 144

Register Name	Address	Permission	Description
PERI_MS_PPU_FX144_SL_ADDR	0x40022C00	FULL	Slave region, base address
PERI_MS_PPU_FX144_SL_SIZE	0x40022C04	FULL	Slave region, size
PERI_MS_PPU_FX144_SL_ATT0	0x40022C10	FULL	Slave attributes 0
PERI_MS_PPU_FX144_SL_ATT1	0x40022C14	FULL	Slave attributes 1
PERI_MS_PPU_FX144_SL_ATT2	0x40022C18	FULL	Slave attributes 2
PERI_MS_PPU_FX144_SL_ATT3	0x40022C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX144_MS_ADDR	0x40022C20	FULL	Master region, base address
PERI_MS_PPU_FX144_MS_SIZE	0x40022C24	FULL	Master region, size
PERI_MS_PPU_FX144_MS_ATT0	0x40022C30	FULL	Master attributes 0
PERI_MS_PPU_FX144_MS_ATT1	0x40022C34	FULL	Master attributes 1
PERI_MS_PPU_FX144_MS_ATT2	0x40022C38	FULL	Master attributes 2
PERI_MS_PPU_FX144_MS_ATT3	0x40022C3C	FULL	Master attributes 3

21.162 PPU_FX 145

Register Name	Address	Permission	Description
PERI_MS_PPU_FX145_SL_ADDR	0x40022C40	FULL	Slave region, base address
PERI_MS_PPU_FX145_SL_SIZE	0x40022C44	FULL	Slave region, size
PERI_MS_PPU_FX145_SL_ATT0	0x40022C50	FULL	Slave attributes 0
PERI_MS_PPU_FX145_SL_ATT1	0x40022C54	FULL	Slave attributes 1
PERI_MS_PPU_FX145_SL_ATT2	0x40022C58	FULL	Slave attributes 2
PERI_MS_PPU_FX145_SL_ATT3	0x40022C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX145_MS_ADDR	0x40022C60	FULL	Master region, base address
PERI_MS_PPU_FX145_MS_SIZE	0x40022C64	FULL	Master region, size
PERI_MS_PPU_FX145_MS_ATT0	0x40022C70	FULL	Master attributes 0
PERI_MS_PPU_FX145_MS_ATT1	0x40022C74	FULL	Master attributes 1
PERI_MS_PPU_FX145_MS_ATT2	0x40022C78	FULL	Master attributes 2
PERI_MS_PPU_FX145_MS_ATT3	0x40022C7C	FULL	Master attributes 3

21.163 PPU_FX 146

Register Name	Address	Permission	Description
PERI_MS_PPU_FX146_SL_ADDR	0x40022C80	FULL	Slave region, base address
PERI_MS_PPU_FX146_SL_SIZE	0x40022C84	FULL	Slave region, size
PERI_MS_PPU_FX146_SL_ATT0	0x40022C90	FULL	Slave attributes 0
PERI_MS_PPU_FX146_SL_ATT1	0x40022C94	FULL	Slave attributes 1
PERI_MS_PPU_FX146_SL_ATT2	0x40022C98	FULL	Slave attributes 2
PERI_MS_PPU_FX146_SL_ATT3	0x40022C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX146_MS_ADDR	0x40022CA0	FULL	Master region, base address
PERI_MS_PPU_FX146_MS_SIZE	0x40022CA4	FULL	Master region, size
PERI_MS_PPU_FX146_MS_ATT0	0x40022CB0	FULL	Master attributes 0
PERI_MS_PPU_FX146_MS_ATT1	0x40022CB4	FULL	Master attributes 1
PERI_MS_PPU_FX146_MS_ATT2	0x40022CB8	FULL	Master attributes 2
PERI_MS_PPU_FX146_MS_ATT3	0x40022CBC	FULL	Master attributes 3

21.164 PPU_FX 147

Register Name	Address	Permission	Description
PERI_MS_PPU_FX147_SL_ADDR	0x40022CC0	FULL	Slave region, base address
PERI_MS_PPU_FX147_SL_SIZE	0x40022CC4	FULL	Slave region, size
PERI_MS_PPU_FX147_SL_ATT0	0x40022CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX147_SL_ATT1	0x40022CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX147_SL_ATT2	0x40022CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX147_SL_ATT3	0x40022CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX147_MS_ADDR	0x40022CE0	FULL	Master region, base address
PERI_MS_PPU_FX147_MS_SIZE	0x40022CE4	FULL	Master region, size
PERI_MS_PPU_FX147_MS_ATT0	0x40022CF0	FULL	Master attributes 0
PERI_MS_PPU_FX147_MS_ATT1	0x40022CF4	FULL	Master attributes 1
PERI_MS_PPU_FX147_MS_ATT2	0x40022CF8	FULL	Master attributes 2
PERI_MS_PPU_FX147_MS_ATT3	0x40022CFC	FULL	Master attributes 3

21.165 PPU_FX 148

Register Name	Address	Permission	Description
PERI_MS_PPU_FX148_SL_ADDR	0x40022D00	FULL	Slave region, base address
PERI_MS_PPU_FX148_SL_SIZE	0x40022D04	FULL	Slave region, size
PERI_MS_PPU_FX148_SL_ATT0	0x40022D10	FULL	Slave attributes 0
PERI_MS_PPU_FX148_SL_ATT1	0x40022D14	FULL	Slave attributes 1
PERI_MS_PPU_FX148_SL_ATT2	0x40022D18	FULL	Slave attributes 2
PERI_MS_PPU_FX148_SL_ATT3	0x40022D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX148_MS_ADDR	0x40022D20	FULL	Master region, base address
PERI_MS_PPU_FX148_MS_SIZE	0x40022D24	FULL	Master region, size
PERI_MS_PPU_FX148_MS_ATT0	0x40022D30	FULL	Master attributes 0
PERI_MS_PPU_FX148_MS_ATT1	0x40022D34	FULL	Master attributes 1
PERI_MS_PPU_FX148_MS_ATT2	0x40022D38	FULL	Master attributes 2
PERI_MS_PPU_FX148_MS_ATT3	0x40022D3C	FULL	Master attributes 3

21.166 PPU_FX 149

Register Name	Address	Permission	Description
PERI_MS_PPU_FX149_SL_ADDR	0x40022D40	FULL	Slave region, base address
PERI_MS_PPU_FX149_SL_SIZE	0x40022D44	FULL	Slave region, size
PERI_MS_PPU_FX149_SL_ATT0	0x40022D50	FULL	Slave attributes 0
PERI_MS_PPU_FX149_SL_ATT1	0x40022D54	FULL	Slave attributes 1
PERI_MS_PPU_FX149_SL_ATT2	0x40022D58	FULL	Slave attributes 2
PERI_MS_PPU_FX149_SL_ATT3	0x40022D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX149_MS_ADDR	0x40022D60	FULL	Master region, base address
PERI_MS_PPU_FX149_MS_SIZE	0x40022D64	FULL	Master region, size
PERI_MS_PPU_FX149_MS_ATT0	0x40022D70	FULL	Master attributes 0
PERI_MS_PPU_FX149_MS_ATT1	0x40022D74	FULL	Master attributes 1
PERI_MS_PPU_FX149_MS_ATT2	0x40022D78	FULL	Master attributes 2
PERI_MS_PPU_FX149_MS_ATT3	0x40022D7C	FULL	Master attributes 3

21.167 PPU_FX 150

Register Name	Address	Permission	Description
PERI_MS_PPU_FX150_SL_ADDR	0x40022D80	FULL	Slave region, base address
PERI_MS_PPU_FX150_SL_SIZE	0x40022D84	FULL	Slave region, size
PERI_MS_PPU_FX150_SL_ATT0	0x40022D90	FULL	Slave attributes 0
PERI_MS_PPU_FX150_SL_ATT1	0x40022D94	FULL	Slave attributes 1
PERI_MS_PPU_FX150_SL_ATT2	0x40022D98	FULL	Slave attributes 2
PERI_MS_PPU_FX150_SL_ATT3	0x40022D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX150_MS_ADDR	0x40022DA0	FULL	Master region, base address
PERI_MS_PPU_FX150_MS_SIZE	0x40022DA4	FULL	Master region, size
PERI_MS_PPU_FX150_MS_ATT0	0x40022DB0	FULL	Master attributes 0
PERI_MS_PPU_FX150_MS_ATT1	0x40022DB4	FULL	Master attributes 1
PERI_MS_PPU_FX150_MS_ATT2	0x40022DB8	FULL	Master attributes 2
PERI_MS_PPU_FX150_MS_ATT3	0x40022DBC	FULL	Master attributes 3

21.168 PPU_FX 151

Register Name	Address	Permission	Description
PERI_MS_PPU_FX151_SL_ADDR	0x40022DC0	FULL	Slave region, base address
PERI_MS_PPU_FX151_SL_SIZE	0x40022DC4	FULL	Slave region, size
PERI_MS_PPU_FX151_SL_ATT0	0x40022DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX151_SL_ATT1	0x40022DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX151_SL_ATT2	0x40022DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX151_SL_ATT3	0x40022DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX151_MS_ADDR	0x40022DE0	FULL	Master region, base address
PERI_MS_PPU_FX151_MS_SIZE	0x40022DE4	FULL	Master region, size
PERI_MS_PPU_FX151_MS_ATT0	0x40022DF0	FULL	Master attributes 0
PERI_MS_PPU_FX151_MS_ATT1	0x40022DF4	FULL	Master attributes 1
PERI_MS_PPU_FX151_MS_ATT2	0x40022DF8	FULL	Master attributes 2
PERI_MS_PPU_FX151_MS_ATT3	0x40022DFC	FULL	Master attributes 3

21.169 PPU_FX 152

Register Name	Address	Permission	Description
PERI_MS_PPU_FX152_SL_ADDR	0x40022E00	FULL	Slave region, base address
PERI_MS_PPU_FX152_SL_SIZE	0x40022E04	FULL	Slave region, size
PERI_MS_PPU_FX152_SL_ATT0	0x40022E10	FULL	Slave attributes 0
PERI_MS_PPU_FX152_SL_ATT1	0x40022E14	FULL	Slave attributes 1
PERI_MS_PPU_FX152_SL_ATT2	0x40022E18	FULL	Slave attributes 2
PERI_MS_PPU_FX152_SL_ATT3	0x40022E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX152_MS_ADDR	0x40022E20	FULL	Master region, base address
PERI_MS_PPU_FX152_MS_SIZE	0x40022E24	FULL	Master region, size
PERI_MS_PPU_FX152_MS_ATT0	0x40022E30	FULL	Master attributes 0
PERI_MS_PPU_FX152_MS_ATT1	0x40022E34	FULL	Master attributes 1
PERI_MS_PPU_FX152_MS_ATT2	0x40022E38	FULL	Master attributes 2
PERI_MS_PPU_FX152_MS_ATT3	0x40022E3C	FULL	Master attributes 3

21.170 PPU_FX 153

Register Name	Address	Permission	Description
PERI_MS_PPU_FX153_SL_ADDR	0x40022E40	FULL	Slave region, base address
PERI_MS_PPU_FX153_SL_SIZE	0x40022E44	FULL	Slave region, size
PERI_MS_PPU_FX153_SL_ATT0	0x40022E50	FULL	Slave attributes 0
PERI_MS_PPU_FX153_SL_ATT1	0x40022E54	FULL	Slave attributes 1
PERI_MS_PPU_FX153_SL_ATT2	0x40022E58	FULL	Slave attributes 2
PERI_MS_PPU_FX153_SL_ATT3	0x40022E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX153_MS_ADDR	0x40022E60	FULL	Master region, base address
PERI_MS_PPU_FX153_MS_SIZE	0x40022E64	FULL	Master region, size
PERI_MS_PPU_FX153_MS_ATT0	0x40022E70	FULL	Master attributes 0
PERI_MS_PPU_FX153_MS_ATT1	0x40022E74	FULL	Master attributes 1
PERI_MS_PPU_FX153_MS_ATT2	0x40022E78	FULL	Master attributes 2
PERI_MS_PPU_FX153_MS_ATT3	0x40022E7C	FULL	Master attributes 3

21.171 PPU_FX 154

Register Name	Address	Permission	Description
PERI_MS_PPU_FX154_SL_ADDR	0x40022E80	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX154_SL_SIZE	0x40022E84	FULL	Slave region, size
PERI_MS_PPU_FX154_SL_ATT0	0x40022E90	FULL	Slave attributes 0
PERI_MS_PPU_FX154_SL_ATT1	0x40022E94	FULL	Slave attributes 1
PERI_MS_PPU_FX154_SL_ATT2	0x40022E98	FULL	Slave attributes 2
PERI_MS_PPU_FX154_SL_ATT3	0x40022E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX154_MS_ADDR	0x40022EA0	FULL	Master region, base address
PERI_MS_PPU_FX154_MS_SIZE	0x40022EA4	FULL	Master region, size
PERI_MS_PPU_FX154_MS_ATT0	0x40022EB0	FULL	Master attributes 0
PERI_MS_PPU_FX154_MS_ATT1	0x40022EB4	FULL	Master attributes 1
PERI_MS_PPU_FX154_MS_ATT2	0x40022EB8	FULL	Master attributes 2
PERI_MS_PPU_FX154_MS_ATT3	0x40022EBC	FULL	Master attributes 3

21.172 PPU_FX 155

Register Name	Address	Permission	Description
PERI_MS_PPU_FX155_SL_ADDR	0x40022EC0	FULL	Slave region, base address
PERI_MS_PPU_FX155_SL_SIZE	0x40022EC4	FULL	Slave region, size
PERI_MS_PPU_FX155_SL_ATT0	0x40022ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX155_SL_ATT1	0x40022ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX155_SL_ATT2	0x40022ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX155_SL_ATT3	0x40022EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX155_MS_ADDR	0x40022EE0	FULL	Master region, base address
PERI_MS_PPU_FX155_MS_SIZE	0x40022EE4	FULL	Master region, size
PERI_MS_PPU_FX155_MS_ATT0	0x40022EF0	FULL	Master attributes 0
PERI_MS_PPU_FX155_MS_ATT1	0x40022EF4	FULL	Master attributes 1
PERI_MS_PPU_FX155_MS_ATT2	0x40022EF8	FULL	Master attributes 2
PERI_MS_PPU_FX155_MS_ATT3	0x40022EFC	FULL	Master attributes 3

21.173 PPU_FX 156

Register Name	Address	Permission	Description
PERI_MS_PPU_FX156_SL_ADDR	0x40022F00	FULL	Slave region, base address
PERI_MS_PPU_FX156_SL_SIZE	0x40022F04	FULL	Slave region, size
PERI_MS_PPU_FX156_SL_ATT0	0x40022F10	FULL	Slave attributes 0
PERI_MS_PPU_FX156_SL_ATT1	0x40022F14	FULL	Slave attributes 1
PERI_MS_PPU_FX156_SL_ATT2	0x40022F18	FULL	Slave attributes 2
PERI_MS_PPU_FX156_SL_ATT3	0x40022F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX156_MS_ADDR	0x40022F20	FULL	Master region, base address
PERI_MS_PPU_FX156_MS_SIZE	0x40022F24	FULL	Master region, size
PERI_MS_PPU_FX156_MS_ATT0	0x40022F30	FULL	Master attributes 0
PERI_MS_PPU_FX156_MS_ATT1	0x40022F34	FULL	Master attributes 1
PERI_MS_PPU_FX156_MS_ATT2	0x40022F38	FULL	Master attributes 2
PERI_MS_PPU_FX156_MS_ATT3	0x40022F3C	FULL	Master attributes 3

21.174 PPU_FX 157

Register Name	Address	Permission	Description
PERI_MS_PPU_FX157_SL_ADDR	0x40022F40	FULL	Slave region, base address
PERI_MS_PPU_FX157_SL_SIZE	0x40022F44	FULL	Slave region, size
PERI_MS_PPU_FX157_SL_ATT0	0x40022F50	FULL	Slave attributes 0
PERI_MS_PPU_FX157_SL_ATT1	0x40022F54	FULL	Slave attributes 1
PERI_MS_PPU_FX157_SL_ATT2	0x40022F58	FULL	Slave attributes 2
PERI_MS_PPU_FX157_SL_ATT3	0x40022F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX157_MS_ADDR	0x40022F60	FULL	Master region, base address
PERI_MS_PPU_FX157_MS_SIZE	0x40022F64	FULL	Master region, size
PERI_MS_PPU_FX157_MS_ATT0	0x40022F70	FULL	Master attributes 0
PERI_MS_PPU_FX157_MS_ATT1	0x40022F74	FULL	Master attributes 1
PERI_MS_PPU_FX157_MS_ATT2	0x40022F78	FULL	Master attributes 2
PERI_MS_PPU_FX157_MS_ATT3	0x40022F7C	FULL	Master attributes 3

21.175 PPU_FX 158

Register Name	Address	Permission	Description
PERI_MS_PPU_FX158_SL_ADDR	0x40022F80	FULL	Slave region, base address
PERI_MS_PPU_FX158_SL_SIZE	0x40022F84	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX158_SL_ATT0	0x40022F90	FULL	Slave attributes 0
PERI_MS_PPU_FX158_SL_ATT1	0x40022F94	FULL	Slave attributes 1
PERI_MS_PPU_FX158_SL_ATT2	0x40022F98	FULL	Slave attributes 2
PERI_MS_PPU_FX158_SL_ATT3	0x40022F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX158_MS_ADDR	0x40022FA0	FULL	Master region, base address
PERI_MS_PPU_FX158_MS_SIZE	0x40022FA4	FULL	Master region, size
PERI_MS_PPU_FX158_MS_ATT0	0x40022FB0	FULL	Master attributes 0
PERI_MS_PPU_FX158_MS_ATT1	0x40022FB4	FULL	Master attributes 1
PERI_MS_PPU_FX158_MS_ATT2	0x40022FB8	FULL	Master attributes 2
PERI_MS_PPU_FX158_MS_ATT3	0x40022FBC	FULL	Master attributes 3

21.176 PPU_FX 159

Register Name	Address	Permission	Description
PERI_MS_PPU_FX159_SL_ADDR	0x40022FC0	FULL	Slave region, base address
PERI_MS_PPU_FX159_SL_SIZE	0x40022FC4	FULL	Slave region, size
PERI_MS_PPU_FX159_SL_ATT0	0x40022FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX159_SL_ATT1	0x40022FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX159_SL_ATT2	0x40022FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX159_SL_ATT3	0x40022FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX159_MS_ADDR	0x40022FE0	FULL	Master region, base address
PERI_MS_PPU_FX159_MS_SIZE	0x40022FE4	FULL	Master region, size
PERI_MS_PPU_FX159_MS_ATT0	0x40022FF0	FULL	Master attributes 0
PERI_MS_PPU_FX159_MS_ATT1	0x40022FF4	FULL	Master attributes 1
PERI_MS_PPU_FX159_MS_ATT2	0x40022FF8	FULL	Master attributes 2
PERI_MS_PPU_FX159_MS_ATT3	0x40022FFC	FULL	Master attributes 3

21.177 PPU_FX 160

Register Name	Address	Permission	Description
PERI_MS_PPU_FX160_SL_ADDR	0x40023000	FULL	Slave region, base address
PERI_MS_PPU_FX160_SL_SIZE	0x40023004	FULL	Slave region, size
PERI_MS_PPU_FX160_SL_ATT0	0x40023010	FULL	Slave attributes 0
PERI_MS_PPU_FX160_SL_ATT1	0x40023014	FULL	Slave attributes 1
PERI_MS_PPU_FX160_SL_ATT2	0x40023018	FULL	Slave attributes 2
PERI_MS_PPU_FX160_SL_ATT3	0x4002301C	FULL	Slave attributes 3
PERI_MS_PPU_FX160_MS_ADDR	0x40023020	FULL	Master region, base address
PERI_MS_PPU_FX160_MS_SIZE	0x40023024	FULL	Master region, size
PERI_MS_PPU_FX160_MS_ATT0	0x40023030	FULL	Master attributes 0
PERI_MS_PPU_FX160_MS_ATT1	0x40023034	FULL	Master attributes 1
PERI_MS_PPU_FX160_MS_ATT2	0x40023038	FULL	Master attributes 2
PERI_MS_PPU_FX160_MS_ATT3	0x4002303C	FULL	Master attributes 3

21.178 PPU_FX 161

Register Name	Address	Permission	Description
PERI_MS_PPU_FX161_SL_ADDR	0x40023040	FULL	Slave region, base address
PERI_MS_PPU_FX161_SL_SIZE	0x40023044	FULL	Slave region, size
PERI_MS_PPU_FX161_SL_ATT0	0x40023050	FULL	Slave attributes 0
PERI_MS_PPU_FX161_SL_ATT1	0x40023054	FULL	Slave attributes 1
PERI_MS_PPU_FX161_SL_ATT2	0x40023058	FULL	Slave attributes 2
PERI_MS_PPU_FX161_SL_ATT3	0x4002305C	FULL	Slave attributes 3
PERI_MS_PPU_FX161_MS_ADDR	0x40023060	FULL	Master region, base address
PERI_MS_PPU_FX161_MS_SIZE	0x40023064	FULL	Master region, size
PERI_MS_PPU_FX161_MS_ATT0	0x40023070	FULL	Master attributes 0
PERI_MS_PPU_FX161_MS_ATT1	0x40023074	FULL	Master attributes 1
PERI_MS_PPU_FX161_MS_ATT2	0x40023078	FULL	Master attributes 2
PERI_MS_PPU_FX161_MS_ATT3	0x4002307C	FULL	Master attributes 3

21.179 PPU_FX 162

Register Name	Address	Permission	Description
PERI_MS_PPU_FX162_SL_ADDR	0x40023080	FULL	Slave region, base address
PERI_MS_PPU_FX162_SL_SIZE	0x40023084	FULL	Slave region, size
PERI_MS_PPU_FX162_SL_ATT0	0x40023090	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX162_SL_ATT1	0x40023094	FULL	Slave attributes 1
PERI_MS_PPU_FX162_SL_ATT2	0x40023098	FULL	Slave attributes 2
PERI_MS_PPU_FX162_SL_ATT3	0x4002309C	FULL	Slave attributes 3
PERI_MS_PPU_FX162_MS_ADDR	0x400230A0	FULL	Master region, base address
PERI_MS_PPU_FX162_MS_SIZE	0x400230A4	FULL	Master region, size
PERI_MS_PPU_FX162_MS_ATT0	0x400230B0	FULL	Master attributes 0
PERI_MS_PPU_FX162_MS_ATT1	0x400230B4	FULL	Master attributes 1
PERI_MS_PPU_FX162_MS_ATT2	0x400230B8	FULL	Master attributes 2
PERI_MS_PPU_FX162_MS_ATT3	0x400230BC	FULL	Master attributes 3

21.180 PPU_FX 163

Register Name	Address	Permission	Description
PERI_MS_PPU_FX163_SL_ADDR	0x400230C0	FULL	Slave region, base address
PERI_MS_PPU_FX163_SL_SIZE	0x400230C4	FULL	Slave region, size
PERI_MS_PPU_FX163_SL_ATT0	0x400230D0	FULL	Slave attributes 0
PERI_MS_PPU_FX163_SL_ATT1	0x400230D4	FULL	Slave attributes 1
PERI_MS_PPU_FX163_SL_ATT2	0x400230D8	FULL	Slave attributes 2
PERI_MS_PPU_FX163_SL_ATT3	0x400230DC	FULL	Slave attributes 3
PERI_MS_PPU_FX163_MS_ADDR	0x400230E0	FULL	Master region, base address
PERI_MS_PPU_FX163_MS_SIZE	0x400230E4	FULL	Master region, size
PERI_MS_PPU_FX163_MS_ATT0	0x400230F0	FULL	Master attributes 0
PERI_MS_PPU_FX163_MS_ATT1	0x400230F4	FULL	Master attributes 1
PERI_MS_PPU_FX163_MS_ATT2	0x400230F8	FULL	Master attributes 2
PERI_MS_PPU_FX163_MS_ATT3	0x400230FC	FULL	Master attributes 3

21.181 PPU_FX 164

Register Name	Address	Permission	Description
PERI_MS_PPU_FX164_SL_ADDR	0x40023100	FULL	Slave region, base address
PERI_MS_PPU_FX164_SL_SIZE	0x40023104	FULL	Slave region, size
PERI_MS_PPU_FX164_SL_ATT0	0x40023110	FULL	Slave attributes 0
PERI_MS_PPU_FX164_SL_ATT1	0x40023114	FULL	Slave attributes 1
PERI_MS_PPU_FX164_SL_ATT2	0x40023118	FULL	Slave attributes 2
PERI_MS_PPU_FX164_SL_ATT3	0x4002311C	FULL	Slave attributes 3
PERI_MS_PPU_FX164_MS_ADDR	0x40023120	FULL	Master region, base address
PERI_MS_PPU_FX164_MS_SIZE	0x40023124	FULL	Master region, size
PERI_MS_PPU_FX164_MS_ATT0	0x40023130	FULL	Master attributes 0
PERI_MS_PPU_FX164_MS_ATT1	0x40023134	FULL	Master attributes 1
PERI_MS_PPU_FX164_MS_ATT2	0x40023138	FULL	Master attributes 2
PERI_MS_PPU_FX164_MS_ATT3	0x4002313C	FULL	Master attributes 3

21.182 PPU_FX 165

Register Name	Address	Permission	Description
PERI_MS_PPU_FX165_SL_ADDR	0x40023140	FULL	Slave region, base address
PERI_MS_PPU_FX165_SL_SIZE	0x40023144	FULL	Slave region, size
PERI_MS_PPU_FX165_SL_ATT0	0x40023150	FULL	Slave attributes 0
PERI_MS_PPU_FX165_SL_ATT1	0x40023154	FULL	Slave attributes 1
PERI_MS_PPU_FX165_SL_ATT2	0x40023158	FULL	Slave attributes 2
PERI_MS_PPU_FX165_SL_ATT3	0x4002315C	FULL	Slave attributes 3
PERI_MS_PPU_FX165_MS_ADDR	0x40023160	FULL	Master region, base address
PERI_MS_PPU_FX165_MS_SIZE	0x40023164	FULL	Master region, size
PERI_MS_PPU_FX165_MS_ATT0	0x40023170	FULL	Master attributes 0
PERI_MS_PPU_FX165_MS_ATT1	0x40023174	FULL	Master attributes 1
PERI_MS_PPU_FX165_MS_ATT2	0x40023178	FULL	Master attributes 2
PERI_MS_PPU_FX165_MS_ATT3	0x4002317C	FULL	Master attributes 3

21.183 PPU_FX 166

Register Name	Address	Permission	Description
PERI_MS_PPU_FX166_SL_ADDR	0x40023180	FULL	Slave region, base address
PERI_MS_PPU_FX166_SL_SIZE	0x40023184	FULL	Slave region, size
PERI_MS_PPU_FX166_SL_ATT0	0x40023190	FULL	Slave attributes 0
PERI_MS_PPU_FX166_SL_ATT1	0x40023194	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX166_SL_ATT2	0x40023198	FULL	Slave attributes 2
PERI_MS_PPU_FX166_SL_ATT3	0x4002319C	FULL	Slave attributes 3
PERI_MS_PPU_FX166_MS_ADDR	0x400231A0	FULL	Master region, base address
PERI_MS_PPU_FX166_MS_SIZE	0x400231A4	FULL	Master region, size
PERI_MS_PPU_FX166_MS_ATT0	0x400231B0	FULL	Master attributes 0
PERI_MS_PPU_FX166_MS_ATT1	0x400231B4	FULL	Master attributes 1
PERI_MS_PPU_FX166_MS_ATT2	0x400231B8	FULL	Master attributes 2
PERI_MS_PPU_FX166_MS_ATT3	0x400231BC	FULL	Master attributes 3

21.184 PPU_FX 167

Register Name	Address	Permission	Description
PERI_MS_PPU_FX167_SL_ADDR	0x400231C0	FULL	Slave region, base address
PERI_MS_PPU_FX167_SL_SIZE	0x400231C4	FULL	Slave region, size
PERI_MS_PPU_FX167_SL_ATT0	0x400231D0	FULL	Slave attributes 0
PERI_MS_PPU_FX167_SL_ATT1	0x400231D4	FULL	Slave attributes 1
PERI_MS_PPU_FX167_SL_ATT2	0x400231D8	FULL	Slave attributes 2
PERI_MS_PPU_FX167_SL_ATT3	0x400231DC	FULL	Slave attributes 3
PERI_MS_PPU_FX167_MS_ADDR	0x400231E0	FULL	Master region, base address
PERI_MS_PPU_FX167_MS_SIZE	0x400231E4	FULL	Master region, size
PERI_MS_PPU_FX167_MS_ATT0	0x400231F0	FULL	Master attributes 0
PERI_MS_PPU_FX167_MS_ATT1	0x400231F4	FULL	Master attributes 1
PERI_MS_PPU_FX167_MS_ATT2	0x400231F8	FULL	Master attributes 2
PERI_MS_PPU_FX167_MS_ATT3	0x400231FC	FULL	Master attributes 3

21.185 PPU_FX 168

Register Name	Address	Permission	Description
PERI_MS_PPU_FX168_SL_ADDR	0x40023200	FULL	Slave region, base address
PERI_MS_PPU_FX168_SL_SIZE	0x40023204	FULL	Slave region, size
PERI_MS_PPU_FX168_SL_ATT0	0x40023210	FULL	Slave attributes 0
PERI_MS_PPU_FX168_SL_ATT1	0x40023214	FULL	Slave attributes 1
PERI_MS_PPU_FX168_SL_ATT2	0x40023218	FULL	Slave attributes 2
PERI_MS_PPU_FX168_SL_ATT3	0x4002321C	FULL	Slave attributes 3
PERI_MS_PPU_FX168_MS_ADDR	0x40023220	FULL	Master region, base address
PERI_MS_PPU_FX168_MS_SIZE	0x40023224	FULL	Master region, size
PERI_MS_PPU_FX168_MS_ATT0	0x40023230	FULL	Master attributes 0
PERI_MS_PPU_FX168_MS_ATT1	0x40023234	FULL	Master attributes 1
PERI_MS_PPU_FX168_MS_ATT2	0x40023238	FULL	Master attributes 2
PERI_MS_PPU_FX168_MS_ATT3	0x4002323C	FULL	Master attributes 3

21.186 PPU_FX 169

Register Name	Address	Permission	Description
PERI_MS_PPU_FX169_SL_ADDR	0x40023240	FULL	Slave region, base address
PERI_MS_PPU_FX169_SL_SIZE	0x40023244	FULL	Slave region, size
PERI_MS_PPU_FX169_SL_ATT0	0x40023250	FULL	Slave attributes 0
PERI_MS_PPU_FX169_SL_ATT1	0x40023254	FULL	Slave attributes 1
PERI_MS_PPU_FX169_SL_ATT2	0x40023258	FULL	Slave attributes 2
PERI_MS_PPU_FX169_SL_ATT3	0x4002325C	FULL	Slave attributes 3
PERI_MS_PPU_FX169_MS_ADDR	0x40023260	FULL	Master region, base address
PERI_MS_PPU_FX169_MS_SIZE	0x40023264	FULL	Master region, size
PERI_MS_PPU_FX169_MS_ATT0	0x40023270	FULL	Master attributes 0
PERI_MS_PPU_FX169_MS_ATT1	0x40023274	FULL	Master attributes 1
PERI_MS_PPU_FX169_MS_ATT2	0x40023278	FULL	Master attributes 2
PERI_MS_PPU_FX169_MS_ATT3	0x4002327C	FULL	Master attributes 3

21.187 PPU_FX 170

Register Name	Address	Permission	Description
PERI_MS_PPU_FX170_SL_ADDR	0x40023280	FULL	Slave region, base address
PERI_MS_PPU_FX170_SL_SIZE	0x40023284	FULL	Slave region, size
PERI_MS_PPU_FX170_SL_ATT0	0x40023290	FULL	Slave attributes 0
PERI_MS_PPU_FX170_SL_ATT1	0x40023294	FULL	Slave attributes 1
PERI_MS_PPU_FX170_SL_ATT2	0x40023298	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX170_SL_ATT3	0x4002329C	FULL	Slave attributes 3
PERI_MS_PPU_FX170_MS_ADDR	0x400232A0	FULL	Master region, base address
PERI_MS_PPU_FX170_MS_SIZE	0x400232A4	FULL	Master region, size
PERI_MS_PPU_FX170_MS_ATT0	0x400232B0	FULL	Master attributes 0
PERI_MS_PPU_FX170_MS_ATT1	0x400232B4	FULL	Master attributes 1
PERI_MS_PPU_FX170_MS_ATT2	0x400232B8	FULL	Master attributes 2
PERI_MS_PPU_FX170_MS_ATT3	0x400232BC	FULL	Master attributes 3

21.188 PPU_FX 171

Register Name	Address	Permission	Description
PERI_MS_PPU_FX171_SL_ADDR	0x400232C0	FULL	Slave region, base address
PERI_MS_PPU_FX171_SL_SIZE	0x400232C4	FULL	Slave region, size
PERI_MS_PPU_FX171_SL_ATT0	0x400232D0	FULL	Slave attributes 0
PERI_MS_PPU_FX171_SL_ATT1	0x400232D4	FULL	Slave attributes 1
PERI_MS_PPU_FX171_SL_ATT2	0x400232D8	FULL	Slave attributes 2
PERI_MS_PPU_FX171_SL_ATT3	0x400232DC	FULL	Slave attributes 3
PERI_MS_PPU_FX171_MS_ADDR	0x400232E0	FULL	Master region, base address
PERI_MS_PPU_FX171_MS_SIZE	0x400232E4	FULL	Master region, size
PERI_MS_PPU_FX171_MS_ATT0	0x400232F0	FULL	Master attributes 0
PERI_MS_PPU_FX171_MS_ATT1	0x400232F4	FULL	Master attributes 1
PERI_MS_PPU_FX171_MS_ATT2	0x400232F8	FULL	Master attributes 2
PERI_MS_PPU_FX171_MS_ATT3	0x400232FC	FULL	Master attributes 3

21.189 PPU_FX 172

Register Name	Address	Permission	Description
PERI_MS_PPU_FX172_SL_ADDR	0x40023300	FULL	Slave region, base address
PERI_MS_PPU_FX172_SL_SIZE	0x40023304	FULL	Slave region, size
PERI_MS_PPU_FX172_SL_ATT0	0x40023310	FULL	Slave attributes 0
PERI_MS_PPU_FX172_SL_ATT1	0x40023314	FULL	Slave attributes 1
PERI_MS_PPU_FX172_SL_ATT2	0x40023318	FULL	Slave attributes 2
PERI_MS_PPU_FX172_SL_ATT3	0x4002331C	FULL	Slave attributes 3
PERI_MS_PPU_FX172_MS_ADDR	0x40023320	FULL	Master region, base address
PERI_MS_PPU_FX172_MS_SIZE	0x40023324	FULL	Master region, size
PERI_MS_PPU_FX172_MS_ATT0	0x40023330	FULL	Master attributes 0
PERI_MS_PPU_FX172_MS_ATT1	0x40023334	FULL	Master attributes 1
PERI_MS_PPU_FX172_MS_ATT2	0x40023338	FULL	Master attributes 2
PERI_MS_PPU_FX172_MS_ATT3	0x4002333C	FULL	Master attributes 3

21.190 PPU_FX 173

Register Name	Address	Permission	Description
PERI_MS_PPU_FX173_SL_ADDR	0x40023340	FULL	Slave region, base address
PERI_MS_PPU_FX173_SL_SIZE	0x40023344	FULL	Slave region, size
PERI_MS_PPU_FX173_SL_ATT0	0x40023350	FULL	Slave attributes 0
PERI_MS_PPU_FX173_SL_ATT1	0x40023354	FULL	Slave attributes 1
PERI_MS_PPU_FX173_SL_ATT2	0x40023358	FULL	Slave attributes 2
PERI_MS_PPU_FX173_SL_ATT3	0x4002335C	FULL	Slave attributes 3
PERI_MS_PPU_FX173_MS_ADDR	0x40023360	FULL	Master region, base address
PERI_MS_PPU_FX173_MS_SIZE	0x40023364	FULL	Master region, size
PERI_MS_PPU_FX173_MS_ATT0	0x40023370	FULL	Master attributes 0
PERI_MS_PPU_FX173_MS_ATT1	0x40023374	FULL	Master attributes 1
PERI_MS_PPU_FX173_MS_ATT2	0x40023378	FULL	Master attributes 2
PERI_MS_PPU_FX173_MS_ATT3	0x4002337C	FULL	Master attributes 3

21.191 PPU_FX 174

Register Name	Address	Permission	Description
PERI_MS_PPU_FX174_SL_ADDR	0x40023380	FULL	Slave region, base address
PERI_MS_PPU_FX174_SL_SIZE	0x40023384	FULL	Slave region, size
PERI_MS_PPU_FX174_SL_ATT0	0x40023390	FULL	Slave attributes 0
PERI_MS_PPU_FX174_SL_ATT1	0x40023394	FULL	Slave attributes 1
PERI_MS_PPU_FX174_SL_ATT2	0x40023398	FULL	Slave attributes 2
PERI_MS_PPU_FX174_SL_ATT3	0x4002339C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX174_MS_ADDR	0x400233A0	FULL	Master region, base address
PERI_MS_PPU_FX174_MS_SIZE	0x400233A4	FULL	Master region, size
PERI_MS_PPU_FX174_MS_ATT0	0x400233B0	FULL	Master attributes 0
PERI_MS_PPU_FX174_MS_ATT1	0x400233B4	FULL	Master attributes 1
PERI_MS_PPU_FX174_MS_ATT2	0x400233B8	FULL	Master attributes 2
PERI_MS_PPU_FX174_MS_ATT3	0x400233BC	FULL	Master attributes 3

21.192 PPU_FX 175

Register Name	Address	Permission	Description
PERI_MS_PPU_FX175_SL_ADDR	0x400233C0	FULL	Slave region, base address
PERI_MS_PPU_FX175_SL_SIZE	0x400233C4	FULL	Slave region, size
PERI_MS_PPU_FX175_SL_ATT0	0x400233D0	FULL	Slave attributes 0
PERI_MS_PPU_FX175_SL_ATT1	0x400233D4	FULL	Slave attributes 1
PERI_MS_PPU_FX175_SL_ATT2	0x400233D8	FULL	Slave attributes 2
PERI_MS_PPU_FX175_SL_ATT3	0x400233DC	FULL	Slave attributes 3
PERI_MS_PPU_FX175_MS_ADDR	0x400233E0	FULL	Master region, base address
PERI_MS_PPU_FX175_MS_SIZE	0x400233E4	FULL	Master region, size
PERI_MS_PPU_FX175_MS_ATT0	0x400233F0	FULL	Master attributes 0
PERI_MS_PPU_FX175_MS_ATT1	0x400233F4	FULL	Master attributes 1
PERI_MS_PPU_FX175_MS_ATT2	0x400233F8	FULL	Master attributes 2
PERI_MS_PPU_FX175_MS_ATT3	0x400233FC	FULL	Master attributes 3

21.193 PPU_FX 176

Register Name	Address	Permission	Description
PERI_MS_PPU_FX176_SL_ADDR	0x40023400	FULL	Slave region, base address
PERI_MS_PPU_FX176_SL_SIZE	0x40023404	FULL	Slave region, size
PERI_MS_PPU_FX176_SL_ATT0	0x40023410	FULL	Slave attributes 0
PERI_MS_PPU_FX176_SL_ATT1	0x40023414	FULL	Slave attributes 1
PERI_MS_PPU_FX176_SL_ATT2	0x40023418	FULL	Slave attributes 2
PERI_MS_PPU_FX176_SL_ATT3	0x4002341C	FULL	Slave attributes 3
PERI_MS_PPU_FX176_MS_ADDR	0x40023420	FULL	Master region, base address
PERI_MS_PPU_FX176_MS_SIZE	0x40023424	FULL	Master region, size
PERI_MS_PPU_FX176_MS_ATT0	0x40023430	FULL	Master attributes 0
PERI_MS_PPU_FX176_MS_ATT1	0x40023434	FULL	Master attributes 1
PERI_MS_PPU_FX176_MS_ATT2	0x40023438	FULL	Master attributes 2
PERI_MS_PPU_FX176_MS_ATT3	0x4002343C	FULL	Master attributes 3

21.194 PPU_FX 177

Register Name	Address	Permission	Description
PERI_MS_PPU_FX177_SL_ADDR	0x40023440	FULL	Slave region, base address
PERI_MS_PPU_FX177_SL_SIZE	0x40023444	FULL	Slave region, size
PERI_MS_PPU_FX177_SL_ATT0	0x40023450	FULL	Slave attributes 0
PERI_MS_PPU_FX177_SL_ATT1	0x40023454	FULL	Slave attributes 1
PERI_MS_PPU_FX177_SL_ATT2	0x40023458	FULL	Slave attributes 2
PERI_MS_PPU_FX177_SL_ATT3	0x4002345C	FULL	Slave attributes 3
PERI_MS_PPU_FX177_MS_ADDR	0x40023460	FULL	Master region, base address
PERI_MS_PPU_FX177_MS_SIZE	0x40023464	FULL	Master region, size
PERI_MS_PPU_FX177_MS_ATT0	0x40023470	FULL	Master attributes 0
PERI_MS_PPU_FX177_MS_ATT1	0x40023474	FULL	Master attributes 1
PERI_MS_PPU_FX177_MS_ATT2	0x40023478	FULL	Master attributes 2
PERI_MS_PPU_FX177_MS_ATT3	0x4002347C	FULL	Master attributes 3

21.195 PPU_FX 178

Register Name	Address	Permission	Description
PERI_MS_PPU_FX178_SL_ADDR	0x40023480	FULL	Slave region, base address
PERI_MS_PPU_FX178_SL_SIZE	0x40023484	FULL	Slave region, size
PERI_MS_PPU_FX178_SL_ATT0	0x40023490	FULL	Slave attributes 0
PERI_MS_PPU_FX178_SL_ATT1	0x40023494	FULL	Slave attributes 1
PERI_MS_PPU_FX178_SL_ATT2	0x40023498	FULL	Slave attributes 2
PERI_MS_PPU_FX178_SL_ATT3	0x4002349C	FULL	Slave attributes 3
PERI_MS_PPU_FX178_MS_ADDR	0x400234A0	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX178_MS_SIZE	0x400234A4	FULL	Master region, size
PERI_MS_PPU_FX178_MS_ATT0	0x400234B0	FULL	Master attributes 0
PERI_MS_PPU_FX178_MS_ATT1	0x400234B4	FULL	Master attributes 1
PERI_MS_PPU_FX178_MS_ATT2	0x400234B8	FULL	Master attributes 2
PERI_MS_PPU_FX178_MS_ATT3	0x400234BC	FULL	Master attributes 3

21.196 PPU_FX 179

Register Name	Address	Permission	Description
PERI_MS_PPU_FX179_SL_ADDR	0x400234C0	FULL	Slave region, base address
PERI_MS_PPU_FX179_SL_SIZE	0x400234C4	FULL	Slave region, size
PERI_MS_PPU_FX179_SL_ATT0	0x400234D0	FULL	Slave attributes 0
PERI_MS_PPU_FX179_SL_ATT1	0x400234D4	FULL	Slave attributes 1
PERI_MS_PPU_FX179_SL_ATT2	0x400234D8	FULL	Slave attributes 2
PERI_MS_PPU_FX179_SL_ATT3	0x400234DC	FULL	Slave attributes 3
PERI_MS_PPU_FX179_MS_ADDR	0x400234E0	FULL	Master region, base address
PERI_MS_PPU_FX179_MS_SIZE	0x400234E4	FULL	Master region, size
PERI_MS_PPU_FX179_MS_ATT0	0x400234F0	FULL	Master attributes 0
PERI_MS_PPU_FX179_MS_ATT1	0x400234F4	FULL	Master attributes 1
PERI_MS_PPU_FX179_MS_ATT2	0x400234F8	FULL	Master attributes 2
PERI_MS_PPU_FX179_MS_ATT3	0x400234FC	FULL	Master attributes 3

21.197 PPU_FX 180

Register Name	Address	Permission	Description
PERI_MS_PPU_FX180_SL_ADDR	0x40023500	FULL	Slave region, base address
PERI_MS_PPU_FX180_SL_SIZE	0x40023504	FULL	Slave region, size
PERI_MS_PPU_FX180_SL_ATT0	0x40023510	FULL	Slave attributes 0
PERI_MS_PPU_FX180_SL_ATT1	0x40023514	FULL	Slave attributes 1
PERI_MS_PPU_FX180_SL_ATT2	0x40023518	FULL	Slave attributes 2
PERI_MS_PPU_FX180_SL_ATT3	0x4002351C	FULL	Slave attributes 3
PERI_MS_PPU_FX180_MS_ADDR	0x40023520	FULL	Master region, base address
PERI_MS_PPU_FX180_MS_SIZE	0x40023524	FULL	Master region, size
PERI_MS_PPU_FX180_MS_ATT0	0x40023530	FULL	Master attributes 0
PERI_MS_PPU_FX180_MS_ATT1	0x40023534	FULL	Master attributes 1
PERI_MS_PPU_FX180_MS_ATT2	0x40023538	FULL	Master attributes 2
PERI_MS_PPU_FX180_MS_ATT3	0x4002353C	FULL	Master attributes 3

21.198 PPU_FX 181

Register Name	Address	Permission	Description
PERI_MS_PPU_FX181_SL_ADDR	0x40023540	FULL	Slave region, base address
PERI_MS_PPU_FX181_SL_SIZE	0x40023544	FULL	Slave region, size
PERI_MS_PPU_FX181_SL_ATT0	0x40023550	FULL	Slave attributes 0
PERI_MS_PPU_FX181_SL_ATT1	0x40023554	FULL	Slave attributes 1
PERI_MS_PPU_FX181_SL_ATT2	0x40023558	FULL	Slave attributes 2
PERI_MS_PPU_FX181_SL_ATT3	0x4002355C	FULL	Slave attributes 3
PERI_MS_PPU_FX181_MS_ADDR	0x40023560	FULL	Master region, base address
PERI_MS_PPU_FX181_MS_SIZE	0x40023564	FULL	Master region, size
PERI_MS_PPU_FX181_MS_ATT0	0x40023570	FULL	Master attributes 0
PERI_MS_PPU_FX181_MS_ATT1	0x40023574	FULL	Master attributes 1
PERI_MS_PPU_FX181_MS_ATT2	0x40023578	FULL	Master attributes 2
PERI_MS_PPU_FX181_MS_ATT3	0x4002357C	FULL	Master attributes 3

21.199 PPU_FX 182

Register Name	Address	Permission	Description
PERI_MS_PPU_FX182_SL_ADDR	0x40023580	FULL	Slave region, base address
PERI_MS_PPU_FX182_SL_SIZE	0x40023584	FULL	Slave region, size
PERI_MS_PPU_FX182_SL_ATT0	0x40023590	FULL	Slave attributes 0
PERI_MS_PPU_FX182_SL_ATT1	0x40023594	FULL	Slave attributes 1
PERI_MS_PPU_FX182_SL_ATT2	0x40023598	FULL	Slave attributes 2
PERI_MS_PPU_FX182_SL_ATT3	0x4002359C	FULL	Slave attributes 3
PERI_MS_PPU_FX182_MS_ADDR	0x400235A0	FULL	Master region, base address
PERI_MS_PPU_FX182_MS_SIZE	0x400235A4	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX182_MS_ATT0	0x400235B0	FULL	Master attributes 0
PERI_MS_PPU_FX182_MS_ATT1	0x400235B4	FULL	Master attributes 1
PERI_MS_PPU_FX182_MS_ATT2	0x400235B8	FULL	Master attributes 2
PERI_MS_PPU_FX182_MS_ATT3	0x400235BC	FULL	Master attributes 3

21.200 PPU_FX 183

Register Name	Address	Permission	Description
PERI_MS_PPU_FX183_SL_ADDR	0x400235C0	FULL	Slave region, base address
PERI_MS_PPU_FX183_SL_SIZE	0x400235C4	FULL	Slave region, size
PERI_MS_PPU_FX183_SL_ATT0	0x400235D0	FULL	Slave attributes 0
PERI_MS_PPU_FX183_SL_ATT1	0x400235D4	FULL	Slave attributes 1
PERI_MS_PPU_FX183_SL_ATT2	0x400235D8	FULL	Slave attributes 2
PERI_MS_PPU_FX183_SL_ATT3	0x400235DC	FULL	Slave attributes 3
PERI_MS_PPU_FX183_MS_ADDR	0x400235E0	FULL	Master region, base address
PERI_MS_PPU_FX183_MS_SIZE	0x400235E4	FULL	Master region, size
PERI_MS_PPU_FX183_MS_ATT0	0x400235F0	FULL	Master attributes 0
PERI_MS_PPU_FX183_MS_ATT1	0x400235F4	FULL	Master attributes 1
PERI_MS_PPU_FX183_MS_ATT2	0x400235F8	FULL	Master attributes 2
PERI_MS_PPU_FX183_MS_ATT3	0x400235FC	FULL	Master attributes 3

21.201 PPU_FX 184

Register Name	Address	Permission	Description
PERI_MS_PPU_FX184_SL_ADDR	0x40023600	FULL	Slave region, base address
PERI_MS_PPU_FX184_SL_SIZE	0x40023604	FULL	Slave region, size
PERI_MS_PPU_FX184_SL_ATT0	0x40023610	FULL	Slave attributes 0
PERI_MS_PPU_FX184_SL_ATT1	0x40023614	FULL	Slave attributes 1
PERI_MS_PPU_FX184_SL_ATT2	0x40023618	FULL	Slave attributes 2
PERI_MS_PPU_FX184_SL_ATT3	0x4002361C	FULL	Slave attributes 3
PERI_MS_PPU_FX184_MS_ADDR	0x40023620	FULL	Master region, base address
PERI_MS_PPU_FX184_MS_SIZE	0x40023624	FULL	Master region, size
PERI_MS_PPU_FX184_MS_ATT0	0x40023630	FULL	Master attributes 0
PERI_MS_PPU_FX184_MS_ATT1	0x40023634	FULL	Master attributes 1
PERI_MS_PPU_FX184_MS_ATT2	0x40023638	FULL	Master attributes 2
PERI_MS_PPU_FX184_MS_ATT3	0x4002363C	FULL	Master attributes 3

21.202 PPU_FX 185

Register Name	Address	Permission	Description
PERI_MS_PPU_FX185_SL_ADDR	0x40023640	FULL	Slave region, base address
PERI_MS_PPU_FX185_SL_SIZE	0x40023644	FULL	Slave region, size
PERI_MS_PPU_FX185_SL_ATT0	0x40023650	FULL	Slave attributes 0
PERI_MS_PPU_FX185_SL_ATT1	0x40023654	FULL	Slave attributes 1
PERI_MS_PPU_FX185_SL_ATT2	0x40023658	FULL	Slave attributes 2
PERI_MS_PPU_FX185_SL_ATT3	0x4002365C	FULL	Slave attributes 3
PERI_MS_PPU_FX185_MS_ADDR	0x40023660	FULL	Master region, base address
PERI_MS_PPU_FX185_MS_SIZE	0x40023664	FULL	Master region, size
PERI_MS_PPU_FX185_MS_ATT0	0x40023670	FULL	Master attributes 0
PERI_MS_PPU_FX185_MS_ATT1	0x40023674	FULL	Master attributes 1
PERI_MS_PPU_FX185_MS_ATT2	0x40023678	FULL	Master attributes 2
PERI_MS_PPU_FX185_MS_ATT3	0x4002367C	FULL	Master attributes 3

21.203 PPU_FX 186

Register Name	Address	Permission	Description
PERI_MS_PPU_FX186_SL_ADDR	0x40023680	FULL	Slave region, base address
PERI_MS_PPU_FX186_SL_SIZE	0x40023684	FULL	Slave region, size
PERI_MS_PPU_FX186_SL_ATT0	0x40023690	FULL	Slave attributes 0
PERI_MS_PPU_FX186_SL_ATT1	0x40023694	FULL	Slave attributes 1
PERI_MS_PPU_FX186_SL_ATT2	0x40023698	FULL	Slave attributes 2
PERI_MS_PPU_FX186_SL_ATT3	0x4002369C	FULL	Slave attributes 3
PERI_MS_PPU_FX186_MS_ADDR	0x400236A0	FULL	Master region, base address
PERI_MS_PPU_FX186_MS_SIZE	0x400236A4	FULL	Master region, size
PERI_MS_PPU_FX186_MS_ATT0	0x400236B0	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX186_MS_ATT1	0x400236B4	FULL	Master attributes 1
PERI_MS_PPU_FX186_MS_ATT2	0x400236B8	FULL	Master attributes 2
PERI_MS_PPU_FX186_MS_ATT3	0x400236BC	FULL	Master attributes 3

21.204 PPU_FX 187

Register Name	Address	Permission	Description
PERI_MS_PPU_FX187_SL_ADDR	0x400236C0	FULL	Slave region, base address
PERI_MS_PPU_FX187_SL_SIZE	0x400236C4	FULL	Slave region, size
PERI_MS_PPU_FX187_SL_ATT0	0x400236D0	FULL	Slave attributes 0
PERI_MS_PPU_FX187_SL_ATT1	0x400236D4	FULL	Slave attributes 1
PERI_MS_PPU_FX187_SL_ATT2	0x400236D8	FULL	Slave attributes 2
PERI_MS_PPU_FX187_SL_ATT3	0x400236DC	FULL	Slave attributes 3
PERI_MS_PPU_FX187_MS_ADDR	0x400236E0	FULL	Master region, base address
PERI_MS_PPU_FX187_MS_SIZE	0x400236E4	FULL	Master region, size
PERI_MS_PPU_FX187_MS_ATT0	0x400236F0	FULL	Master attributes 0
PERI_MS_PPU_FX187_MS_ATT1	0x400236F4	FULL	Master attributes 1
PERI_MS_PPU_FX187_MS_ATT2	0x400236F8	FULL	Master attributes 2
PERI_MS_PPU_FX187_MS_ATT3	0x400236FC	FULL	Master attributes 3

21.205 PPU_FX 188

Register Name	Address	Permission	Description
PERI_MS_PPU_FX188_SL_ADDR	0x40023700	FULL	Slave region, base address
PERI_MS_PPU_FX188_SL_SIZE	0x40023704	FULL	Slave region, size
PERI_MS_PPU_FX188_SL_ATT0	0x40023710	FULL	Slave attributes 0
PERI_MS_PPU_FX188_SL_ATT1	0x40023714	FULL	Slave attributes 1
PERI_MS_PPU_FX188_SL_ATT2	0x40023718	FULL	Slave attributes 2
PERI_MS_PPU_FX188_SL_ATT3	0x4002371C	FULL	Slave attributes 3
PERI_MS_PPU_FX188_MS_ADDR	0x40023720	FULL	Master region, base address
PERI_MS_PPU_FX188_MS_SIZE	0x40023724	FULL	Master region, size
PERI_MS_PPU_FX188_MS_ATT0	0x40023730	FULL	Master attributes 0
PERI_MS_PPU_FX188_MS_ATT1	0x40023734	FULL	Master attributes 1
PERI_MS_PPU_FX188_MS_ATT2	0x40023738	FULL	Master attributes 2
PERI_MS_PPU_FX188_MS_ATT3	0x4002373C	FULL	Master attributes 3

21.206 PPU_FX 189

Register Name	Address	Permission	Description
PERI_MS_PPU_FX189_SL_ADDR	0x40023740	FULL	Slave region, base address
PERI_MS_PPU_FX189_SL_SIZE	0x40023744	FULL	Slave region, size
PERI_MS_PPU_FX189_SL_ATT0	0x40023750	FULL	Slave attributes 0
PERI_MS_PPU_FX189_SL_ATT1	0x40023754	FULL	Slave attributes 1
PERI_MS_PPU_FX189_SL_ATT2	0x40023758	FULL	Slave attributes 2
PERI_MS_PPU_FX189_SL_ATT3	0x4002375C	FULL	Slave attributes 3
PERI_MS_PPU_FX189_MS_ADDR	0x40023760	FULL	Master region, base address
PERI_MS_PPU_FX189_MS_SIZE	0x40023764	FULL	Master region, size
PERI_MS_PPU_FX189_MS_ATT0	0x40023770	FULL	Master attributes 0
PERI_MS_PPU_FX189_MS_ATT1	0x40023774	FULL	Master attributes 1
PERI_MS_PPU_FX189_MS_ATT2	0x40023778	FULL	Master attributes 2
PERI_MS_PPU_FX189_MS_ATT3	0x4002377C	FULL	Master attributes 3

21.207 PPU_FX 190

Register Name	Address	Permission	Description
PERI_MS_PPU_FX190_SL_ADDR	0x40023780	FULL	Slave region, base address
PERI_MS_PPU_FX190_SL_SIZE	0x40023784	FULL	Slave region, size
PERI_MS_PPU_FX190_SL_ATT0	0x40023790	FULL	Slave attributes 0
PERI_MS_PPU_FX190_SL_ATT1	0x40023794	FULL	Slave attributes 1
PERI_MS_PPU_FX190_SL_ATT2	0x40023798	FULL	Slave attributes 2
PERI_MS_PPU_FX190_SL_ATT3	0x4002379C	FULL	Slave attributes 3
PERI_MS_PPU_FX190_MS_ADDR	0x400237A0	FULL	Master region, base address
PERI_MS_PPU_FX190_MS_SIZE	0x400237A4	FULL	Master region, size
PERI_MS_PPU_FX190_MS_ATT0	0x400237B0	FULL	Master attributes 0
PERI_MS_PPU_FX190_MS_ATT1	0x400237B4	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX190_MS_ATT2	0x400237B8	FULL	Master attributes 2
PERI_MS_PPU_FX190_MS_ATT3	0x400237BC	FULL	Master attributes 3

21.208 PPU_FX 191

Register Name	Address	Permission	Description
PERI_MS_PPU_FX191_SL_ADDR	0x400237C0	FULL	Slave region, base address
PERI_MS_PPU_FX191_SL_SIZE	0x400237C4	FULL	Slave region, size
PERI_MS_PPU_FX191_SL_ATT0	0x400237D0	FULL	Slave attributes 0
PERI_MS_PPU_FX191_SL_ATT1	0x400237D4	FULL	Slave attributes 1
PERI_MS_PPU_FX191_SL_ATT2	0x400237D8	FULL	Slave attributes 2
PERI_MS_PPU_FX191_SL_ATT3	0x400237DC	FULL	Slave attributes 3
PERI_MS_PPU_FX191_MS_ADDR	0x400237E0	FULL	Master region, base address
PERI_MS_PPU_FX191_MS_SIZE	0x400237E4	FULL	Master region, size
PERI_MS_PPU_FX191_MS_ATT0	0x400237F0	FULL	Master attributes 0
PERI_MS_PPU_FX191_MS_ATT1	0x400237F4	FULL	Master attributes 1
PERI_MS_PPU_FX191_MS_ATT2	0x400237F8	FULL	Master attributes 2
PERI_MS_PPU_FX191_MS_ATT3	0x400237FC	FULL	Master attributes 3

21.209 PPU_FX 192

Register Name	Address	Permission	Description
PERI_MS_PPU_FX192_SL_ADDR	0x40023800	FULL	Slave region, base address
PERI_MS_PPU_FX192_SL_SIZE	0x40023804	FULL	Slave region, size
PERI_MS_PPU_FX192_SL_ATT0	0x40023810	FULL	Slave attributes 0
PERI_MS_PPU_FX192_SL_ATT1	0x40023814	FULL	Slave attributes 1
PERI_MS_PPU_FX192_SL_ATT2	0x40023818	FULL	Slave attributes 2
PERI_MS_PPU_FX192_SL_ATT3	0x4002381C	FULL	Slave attributes 3
PERI_MS_PPU_FX192_MS_ADDR	0x40023820	FULL	Master region, base address
PERI_MS_PPU_FX192_MS_SIZE	0x40023824	FULL	Master region, size
PERI_MS_PPU_FX192_MS_ATT0	0x40023830	FULL	Master attributes 0
PERI_MS_PPU_FX192_MS_ATT1	0x40023834	FULL	Master attributes 1
PERI_MS_PPU_FX192_MS_ATT2	0x40023838	FULL	Master attributes 2
PERI_MS_PPU_FX192_MS_ATT3	0x4002383C	FULL	Master attributes 3

21.210 PPU_FX 193

Register Name	Address	Permission	Description
PERI_MS_PPU_FX193_SL_ADDR	0x40023840	FULL	Slave region, base address
PERI_MS_PPU_FX193_SL_SIZE	0x40023844	FULL	Slave region, size
PERI_MS_PPU_FX193_SL_ATT0	0x40023850	FULL	Slave attributes 0
PERI_MS_PPU_FX193_SL_ATT1	0x40023854	FULL	Slave attributes 1
PERI_MS_PPU_FX193_SL_ATT2	0x40023858	FULL	Slave attributes 2
PERI_MS_PPU_FX193_SL_ATT3	0x4002385C	FULL	Slave attributes 3
PERI_MS_PPU_FX193_MS_ADDR	0x40023860	FULL	Master region, base address
PERI_MS_PPU_FX193_MS_SIZE	0x40023864	FULL	Master region, size
PERI_MS_PPU_FX193_MS_ATT0	0x40023870	FULL	Master attributes 0
PERI_MS_PPU_FX193_MS_ATT1	0x40023874	FULL	Master attributes 1
PERI_MS_PPU_FX193_MS_ATT2	0x40023878	FULL	Master attributes 2
PERI_MS_PPU_FX193_MS_ATT3	0x4002387C	FULL	Master attributes 3

21.211 PPU_FX 194

Register Name	Address	Permission	Description
PERI_MS_PPU_FX194_SL_ADDR	0x40023880	FULL	Slave region, base address
PERI_MS_PPU_FX194_SL_SIZE	0x40023884	FULL	Slave region, size
PERI_MS_PPU_FX194_SL_ATT0	0x40023890	FULL	Slave attributes 0
PERI_MS_PPU_FX194_SL_ATT1	0x40023894	FULL	Slave attributes 1
PERI_MS_PPU_FX194_SL_ATT2	0x40023898	FULL	Slave attributes 2
PERI_MS_PPU_FX194_SL_ATT3	0x4002389C	FULL	Slave attributes 3
PERI_MS_PPU_FX194_MS_ADDR	0x400238A0	FULL	Master region, base address
PERI_MS_PPU_FX194_MS_SIZE	0x400238A4	FULL	Master region, size
PERI_MS_PPU_FX194_MS_ATT0	0x400238B0	FULL	Master attributes 0
PERI_MS_PPU_FX194_MS_ATT1	0x400238B4	FULL	Master attributes 1
PERI_MS_PPU_FX194_MS_ATT2	0x400238B8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX194_MS_ATT3	0x400238BC	FULL	Master attributes 3

21.212 PPU_FX 195

Register Name	Address	Permission	Description
PERI_MS_PPU_FX195_SL_ADDR	0x400238C0	FULL	Slave region, base address
PERI_MS_PPU_FX195_SL_SIZE	0x400238C4	FULL	Slave region, size
PERI_MS_PPU_FX195_SL_ATT0	0x400238D0	FULL	Slave attributes 0
PERI_MS_PPU_FX195_SL_ATT1	0x400238D4	FULL	Slave attributes 1
PERI_MS_PPU_FX195_SL_ATT2	0x400238D8	FULL	Slave attributes 2
PERI_MS_PPU_FX195_SL_ATT3	0x400238DC	FULL	Slave attributes 3
PERI_MS_PPU_FX195_MS_ADDR	0x400238E0	FULL	Master region, base address
PERI_MS_PPU_FX195_MS_SIZE	0x400238E4	FULL	Master region, size
PERI_MS_PPU_FX195_MS_ATT0	0x400238F0	FULL	Master attributes 0
PERI_MS_PPU_FX195_MS_ATT1	0x400238F4	FULL	Master attributes 1
PERI_MS_PPU_FX195_MS_ATT2	0x400238F8	FULL	Master attributes 2
PERI_MS_PPU_FX195_MS_ATT3	0x400238FC	FULL	Master attributes 3

21.213 PPU_FX 196

Register Name	Address	Permission	Description
PERI_MS_PPU_FX196_SL_ADDR	0x40023900	FULL	Slave region, base address
PERI_MS_PPU_FX196_SL_SIZE	0x40023904	FULL	Slave region, size
PERI_MS_PPU_FX196_SL_ATT0	0x40023910	FULL	Slave attributes 0
PERI_MS_PPU_FX196_SL_ATT1	0x40023914	FULL	Slave attributes 1
PERI_MS_PPU_FX196_SL_ATT2	0x40023918	FULL	Slave attributes 2
PERI_MS_PPU_FX196_SL_ATT3	0x4002391C	FULL	Slave attributes 3
PERI_MS_PPU_FX196_MS_ADDR	0x40023920	FULL	Master region, base address
PERI_MS_PPU_FX196_MS_SIZE	0x40023924	FULL	Master region, size
PERI_MS_PPU_FX196_MS_ATT0	0x40023930	FULL	Master attributes 0
PERI_MS_PPU_FX196_MS_ATT1	0x40023934	FULL	Master attributes 1
PERI_MS_PPU_FX196_MS_ATT2	0x40023938	FULL	Master attributes 2
PERI_MS_PPU_FX196_MS_ATT3	0x4002393C	FULL	Master attributes 3

21.214 PPU_FX 197

Register Name	Address	Permission	Description
PERI_MS_PPU_FX197_SL_ADDR	0x40023940	FULL	Slave region, base address
PERI_MS_PPU_FX197_SL_SIZE	0x40023944	FULL	Slave region, size
PERI_MS_PPU_FX197_SL_ATT0	0x40023950	FULL	Slave attributes 0
PERI_MS_PPU_FX197_SL_ATT1	0x40023954	FULL	Slave attributes 1
PERI_MS_PPU_FX197_SL_ATT2	0x40023958	FULL	Slave attributes 2
PERI_MS_PPU_FX197_SL_ATT3	0x4002395C	FULL	Slave attributes 3
PERI_MS_PPU_FX197_MS_ADDR	0x40023960	FULL	Master region, base address
PERI_MS_PPU_FX197_MS_SIZE	0x40023964	FULL	Master region, size
PERI_MS_PPU_FX197_MS_ATT0	0x40023970	FULL	Master attributes 0
PERI_MS_PPU_FX197_MS_ATT1	0x40023974	FULL	Master attributes 1
PERI_MS_PPU_FX197_MS_ATT2	0x40023978	FULL	Master attributes 2
PERI_MS_PPU_FX197_MS_ATT3	0x4002397C	FULL	Master attributes 3

21.215 PPU_FX 198

Register Name	Address	Permission	Description
PERI_MS_PPU_FX198_SL_ADDR	0x40023980	FULL	Slave region, base address
PERI_MS_PPU_FX198_SL_SIZE	0x40023984	FULL	Slave region, size
PERI_MS_PPU_FX198_SL_ATT0	0x40023990	FULL	Slave attributes 0
PERI_MS_PPU_FX198_SL_ATT1	0x40023994	FULL	Slave attributes 1
PERI_MS_PPU_FX198_SL_ATT2	0x40023998	FULL	Slave attributes 2
PERI_MS_PPU_FX198_SL_ATT3	0x4002399C	FULL	Slave attributes 3
PERI_MS_PPU_FX198_MS_ADDR	0x400239A0	FULL	Master region, base address
PERI_MS_PPU_FX198_MS_SIZE	0x400239A4	FULL	Master region, size
PERI_MS_PPU_FX198_MS_ATT0	0x400239B0	FULL	Master attributes 0
PERI_MS_PPU_FX198_MS_ATT1	0x400239B4	FULL	Master attributes 1
PERI_MS_PPU_FX198_MS_ATT2	0x400239B8	FULL	Master attributes 2
PERI_MS_PPU_FX198_MS_ATT3	0x400239BC	FULL	Master attributes 3

21.216 PPU_FX 199

Register Name	Address	Permission	Description
PERI_MS_PPU_FX199_SL_ADDR	0x400239C0	FULL	Slave region, base address
PERI_MS_PPU_FX199_SL_SIZE	0x400239C4	FULL	Slave region, size
PERI_MS_PPU_FX199_SL_ATT0	0x400239D0	FULL	Slave attributes 0
PERI_MS_PPU_FX199_SL_ATT1	0x400239D4	FULL	Slave attributes 1
PERI_MS_PPU_FX199_SL_ATT2	0x400239D8	FULL	Slave attributes 2
PERI_MS_PPU_FX199_SL_ATT3	0x400239DC	FULL	Slave attributes 3
PERI_MS_PPU_FX199_MS_ADDR	0x400239E0	FULL	Master region, base address
PERI_MS_PPU_FX199_MS_SIZE	0x400239E4	FULL	Master region, size
PERI_MS_PPU_FX199_MS_ATT0	0x400239F0	FULL	Master attributes 0
PERI_MS_PPU_FX199_MS_ATT1	0x400239F4	FULL	Master attributes 1
PERI_MS_PPU_FX199_MS_ATT2	0x400239F8	FULL	Master attributes 2
PERI_MS_PPU_FX199_MS_ATT3	0x400239FC	FULL	Master attributes 3

21.217 PPU_FX 200

Register Name	Address	Permission	Description
PERI_MS_PPU_FX200_SL_ADDR	0x40023A00	FULL	Slave region, base address
PERI_MS_PPU_FX200_SL_SIZE	0x40023A04	FULL	Slave region, size
PERI_MS_PPU_FX200_SL_ATT0	0x40023A10	FULL	Slave attributes 0
PERI_MS_PPU_FX200_SL_ATT1	0x40023A14	FULL	Slave attributes 1
PERI_MS_PPU_FX200_SL_ATT2	0x40023A18	FULL	Slave attributes 2
PERI_MS_PPU_FX200_SL_ATT3	0x40023A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX200_MS_ADDR	0x40023A20	FULL	Master region, base address
PERI_MS_PPU_FX200_MS_SIZE	0x40023A24	FULL	Master region, size
PERI_MS_PPU_FX200_MS_ATT0	0x40023A30	FULL	Master attributes 0
PERI_MS_PPU_FX200_MS_ATT1	0x40023A34	FULL	Master attributes 1
PERI_MS_PPU_FX200_MS_ATT2	0x40023A38	FULL	Master attributes 2
PERI_MS_PPU_FX200_MS_ATT3	0x40023A3C	FULL	Master attributes 3

21.218 PPU_FX 201

Register Name	Address	Permission	Description
PERI_MS_PPU_FX201_SL_ADDR	0x40023A40	FULL	Slave region, base address
PERI_MS_PPU_FX201_SL_SIZE	0x40023A44	FULL	Slave region, size
PERI_MS_PPU_FX201_SL_ATT0	0x40023A50	FULL	Slave attributes 0
PERI_MS_PPU_FX201_SL_ATT1	0x40023A54	FULL	Slave attributes 1
PERI_MS_PPU_FX201_SL_ATT2	0x40023A58	FULL	Slave attributes 2
PERI_MS_PPU_FX201_SL_ATT3	0x40023A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX201_MS_ADDR	0x40023A60	FULL	Master region, base address
PERI_MS_PPU_FX201_MS_SIZE	0x40023A64	FULL	Master region, size
PERI_MS_PPU_FX201_MS_ATT0	0x40023A70	FULL	Master attributes 0
PERI_MS_PPU_FX201_MS_ATT1	0x40023A74	FULL	Master attributes 1
PERI_MS_PPU_FX201_MS_ATT2	0x40023A78	FULL	Master attributes 2
PERI_MS_PPU_FX201_MS_ATT3	0x40023A7C	FULL	Master attributes 3

21.219 PPU_FX 202

Register Name	Address	Permission	Description
PERI_MS_PPU_FX202_SL_ADDR	0x40023A80	FULL	Slave region, base address
PERI_MS_PPU_FX202_SL_SIZE	0x40023A84	FULL	Slave region, size
PERI_MS_PPU_FX202_SL_ATT0	0x40023A90	FULL	Slave attributes 0
PERI_MS_PPU_FX202_SL_ATT1	0x40023A94	FULL	Slave attributes 1
PERI_MS_PPU_FX202_SL_ATT2	0x40023A98	FULL	Slave attributes 2
PERI_MS_PPU_FX202_SL_ATT3	0x40023A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX202_MS_ADDR	0x40023AA0	FULL	Master region, base address
PERI_MS_PPU_FX202_MS_SIZE	0x40023AA4	FULL	Master region, size
PERI_MS_PPU_FX202_MS_ATT0	0x40023AB0	FULL	Master attributes 0
PERI_MS_PPU_FX202_MS_ATT1	0x40023AB4	FULL	Master attributes 1
PERI_MS_PPU_FX202_MS_ATT2	0x40023AB8	FULL	Master attributes 2
PERI_MS_PPU_FX202_MS_ATT3	0x40023ABC	FULL	Master attributes 3

21.220 PPU_FX 203

Register Name	Address	Permission	Description
PERI_MS_PPU_FX203_SL_ADDR	0x40023AC0	FULL	Slave region, base address
PERI_MS_PPU_FX203_SL_SIZE	0x40023AC4	FULL	Slave region, size
PERI_MS_PPU_FX203_SL_ATT0	0x40023AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX203_SL_ATT1	0x40023AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX203_SL_ATT2	0x40023AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX203_SL_ATT3	0x40023ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX203_MS_ADDR	0x40023AE0	FULL	Master region, base address
PERI_MS_PPU_FX203_MS_SIZE	0x40023AE4	FULL	Master region, size
PERI_MS_PPU_FX203_MS_ATT0	0x40023AF0	FULL	Master attributes 0
PERI_MS_PPU_FX203_MS_ATT1	0x40023AF4	FULL	Master attributes 1
PERI_MS_PPU_FX203_MS_ATT2	0x40023AF8	FULL	Master attributes 2
PERI_MS_PPU_FX203_MS_ATT3	0x40023AFC	FULL	Master attributes 3

21.221 PPU_FX 204

Register Name	Address	Permission	Description
PERI_MS_PPU_FX204_SL_ADDR	0x40023B00	FULL	Slave region, base address
PERI_MS_PPU_FX204_SL_SIZE	0x40023B04	FULL	Slave region, size
PERI_MS_PPU_FX204_SL_ATT0	0x40023B10	FULL	Slave attributes 0
PERI_MS_PPU_FX204_SL_ATT1	0x40023B14	FULL	Slave attributes 1
PERI_MS_PPU_FX204_SL_ATT2	0x40023B18	FULL	Slave attributes 2
PERI_MS_PPU_FX204_SL_ATT3	0x40023B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX204_MS_ADDR	0x40023B20	FULL	Master region, base address
PERI_MS_PPU_FX204_MS_SIZE	0x40023B24	FULL	Master region, size
PERI_MS_PPU_FX204_MS_ATT0	0x40023B30	FULL	Master attributes 0
PERI_MS_PPU_FX204_MS_ATT1	0x40023B34	FULL	Master attributes 1
PERI_MS_PPU_FX204_MS_ATT2	0x40023B38	FULL	Master attributes 2
PERI_MS_PPU_FX204_MS_ATT3	0x40023B3C	FULL	Master attributes 3

21.222 PPU_FX 205

Register Name	Address	Permission	Description
PERI_MS_PPU_FX205_SL_ADDR	0x40023B40	FULL	Slave region, base address
PERI_MS_PPU_FX205_SL_SIZE	0x40023B44	FULL	Slave region, size
PERI_MS_PPU_FX205_SL_ATT0	0x40023B50	FULL	Slave attributes 0
PERI_MS_PPU_FX205_SL_ATT1	0x40023B54	FULL	Slave attributes 1
PERI_MS_PPU_FX205_SL_ATT2	0x40023B58	FULL	Slave attributes 2
PERI_MS_PPU_FX205_SL_ATT3	0x40023B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX205_MS_ADDR	0x40023B60	FULL	Master region, base address
PERI_MS_PPU_FX205_MS_SIZE	0x40023B64	FULL	Master region, size
PERI_MS_PPU_FX205_MS_ATT0	0x40023B70	FULL	Master attributes 0
PERI_MS_PPU_FX205_MS_ATT1	0x40023B74	FULL	Master attributes 1
PERI_MS_PPU_FX205_MS_ATT2	0x40023B78	FULL	Master attributes 2
PERI_MS_PPU_FX205_MS_ATT3	0x40023B7C	FULL	Master attributes 3

21.223 PPU_FX 206

Register Name	Address	Permission	Description
PERI_MS_PPU_FX206_SL_ADDR	0x40023B80	FULL	Slave region, base address
PERI_MS_PPU_FX206_SL_SIZE	0x40023B84	FULL	Slave region, size
PERI_MS_PPU_FX206_SL_ATT0	0x40023B90	FULL	Slave attributes 0
PERI_MS_PPU_FX206_SL_ATT1	0x40023B94	FULL	Slave attributes 1
PERI_MS_PPU_FX206_SL_ATT2	0x40023B98	FULL	Slave attributes 2
PERI_MS_PPU_FX206_SL_ATT3	0x40023B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX206_MS_ADDR	0x40023BA0	FULL	Master region, base address
PERI_MS_PPU_FX206_MS_SIZE	0x40023BA4	FULL	Master region, size
PERI_MS_PPU_FX206_MS_ATT0	0x40023BB0	FULL	Master attributes 0
PERI_MS_PPU_FX206_MS_ATT1	0x40023BB4	FULL	Master attributes 1
PERI_MS_PPU_FX206_MS_ATT2	0x40023BB8	FULL	Master attributes 2
PERI_MS_PPU_FX206_MS_ATT3	0x40023BBC	FULL	Master attributes 3

21.224 PPU_FX 207

Register Name	Address	Permission	Description
PERI_MS_PPU_FX207_SL_ADDR	0x40023BC0	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX207_SL_SIZE	0x40023BC4	FULL	Slave region, size
PERI_MS_PPU_FX207_SL_ATT0	0x40023BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX207_SL_ATT1	0x40023BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX207_SL_ATT2	0x40023BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX207_SL_ATT3	0x40023BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX207_MS_ADDR	0x40023BE0	FULL	Master region, base address
PERI_MS_PPU_FX207_MS_SIZE	0x40023BE4	FULL	Master region, size
PERI_MS_PPU_FX207_MS_ATT0	0x40023BF0	FULL	Master attributes 0
PERI_MS_PPU_FX207_MS_ATT1	0x40023BF4	FULL	Master attributes 1
PERI_MS_PPU_FX207_MS_ATT2	0x40023BF8	FULL	Master attributes 2
PERI_MS_PPU_FX207_MS_ATT3	0x40023BFC	FULL	Master attributes 3

21.225 PPU_FX 208

Register Name	Address	Permission	Description
PERI_MS_PPU_FX208_SL_ADDR	0x40023C00	FULL	Slave region, base address
PERI_MS_PPU_FX208_SL_SIZE	0x40023C04	FULL	Slave region, size
PERI_MS_PPU_FX208_SL_ATT0	0x40023C10	FULL	Slave attributes 0
PERI_MS_PPU_FX208_SL_ATT1	0x40023C14	FULL	Slave attributes 1
PERI_MS_PPU_FX208_SL_ATT2	0x40023C18	FULL	Slave attributes 2
PERI_MS_PPU_FX208_SL_ATT3	0x40023C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX208_MS_ADDR	0x40023C20	FULL	Master region, base address
PERI_MS_PPU_FX208_MS_SIZE	0x40023C24	FULL	Master region, size
PERI_MS_PPU_FX208_MS_ATT0	0x40023C30	FULL	Master attributes 0
PERI_MS_PPU_FX208_MS_ATT1	0x40023C34	FULL	Master attributes 1
PERI_MS_PPU_FX208_MS_ATT2	0x40023C38	FULL	Master attributes 2
PERI_MS_PPU_FX208_MS_ATT3	0x40023C3C	FULL	Master attributes 3

21.226 PPU_FX 209

Register Name	Address	Permission	Description
PERI_MS_PPU_FX209_SL_ADDR	0x40023C40	FULL	Slave region, base address
PERI_MS_PPU_FX209_SL_SIZE	0x40023C44	FULL	Slave region, size
PERI_MS_PPU_FX209_SL_ATT0	0x40023C50	FULL	Slave attributes 0
PERI_MS_PPU_FX209_SL_ATT1	0x40023C54	FULL	Slave attributes 1
PERI_MS_PPU_FX209_SL_ATT2	0x40023C58	FULL	Slave attributes 2
PERI_MS_PPU_FX209_SL_ATT3	0x40023C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX209_MS_ADDR	0x40023C60	FULL	Master region, base address
PERI_MS_PPU_FX209_MS_SIZE	0x40023C64	FULL	Master region, size
PERI_MS_PPU_FX209_MS_ATT0	0x40023C70	FULL	Master attributes 0
PERI_MS_PPU_FX209_MS_ATT1	0x40023C74	FULL	Master attributes 1
PERI_MS_PPU_FX209_MS_ATT2	0x40023C78	FULL	Master attributes 2
PERI_MS_PPU_FX209_MS_ATT3	0x40023C7C	FULL	Master attributes 3

21.227 PPU_FX 210

Register Name	Address	Permission	Description
PERI_MS_PPU_FX210_SL_ADDR	0x40023C80	FULL	Slave region, base address
PERI_MS_PPU_FX210_SL_SIZE	0x40023C84	FULL	Slave region, size
PERI_MS_PPU_FX210_SL_ATT0	0x40023C90	FULL	Slave attributes 0
PERI_MS_PPU_FX210_SL_ATT1	0x40023C94	FULL	Slave attributes 1
PERI_MS_PPU_FX210_SL_ATT2	0x40023C98	FULL	Slave attributes 2
PERI_MS_PPU_FX210_SL_ATT3	0x40023C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX210_MS_ADDR	0x40023CA0	FULL	Master region, base address
PERI_MS_PPU_FX210_MS_SIZE	0x40023CA4	FULL	Master region, size
PERI_MS_PPU_FX210_MS_ATT0	0x40023CB0	FULL	Master attributes 0
PERI_MS_PPU_FX210_MS_ATT1	0x40023CB4	FULL	Master attributes 1
PERI_MS_PPU_FX210_MS_ATT2	0x40023CB8	FULL	Master attributes 2
PERI_MS_PPU_FX210_MS_ATT3	0x40023CBC	FULL	Master attributes 3

21.228 PPU_FX 211

Register Name	Address	Permission	Description
PERI_MS_PPU_FX211_SL_ADDR	0x40023CC0	FULL	Slave region, base address
PERI_MS_PPU_FX211_SL_SIZE	0x40023CC4	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX211_SL_ATT0	0x40023CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX211_SL_ATT1	0x40023CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX211_SL_ATT2	0x40023CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX211_SL_ATT3	0x40023CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX211_MS_ADDR	0x40023CE0	FULL	Master region, base address
PERI_MS_PPU_FX211_MS_SIZE	0x40023CE4	FULL	Master region, size
PERI_MS_PPU_FX211_MS_ATT0	0x40023CF0	FULL	Master attributes 0
PERI_MS_PPU_FX211_MS_ATT1	0x40023CF4	FULL	Master attributes 1
PERI_MS_PPU_FX211_MS_ATT2	0x40023CF8	FULL	Master attributes 2
PERI_MS_PPU_FX211_MS_ATT3	0x40023CFC	FULL	Master attributes 3

21.229 PPU_FX 212

Register Name	Address	Permission	Description
PERI_MS_PPU_FX212_SL_ADDR	0x40023D00	FULL	Slave region, base address
PERI_MS_PPU_FX212_SL_SIZE	0x40023D04	FULL	Slave region, size
PERI_MS_PPU_FX212_SL_ATT0	0x40023D10	FULL	Slave attributes 0
PERI_MS_PPU_FX212_SL_ATT1	0x40023D14	FULL	Slave attributes 1
PERI_MS_PPU_FX212_SL_ATT2	0x40023D18	FULL	Slave attributes 2
PERI_MS_PPU_FX212_SL_ATT3	0x40023D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX212_MS_ADDR	0x40023D20	FULL	Master region, base address
PERI_MS_PPU_FX212_MS_SIZE	0x40023D24	FULL	Master region, size
PERI_MS_PPU_FX212_MS_ATT0	0x40023D30	FULL	Master attributes 0
PERI_MS_PPU_FX212_MS_ATT1	0x40023D34	FULL	Master attributes 1
PERI_MS_PPU_FX212_MS_ATT2	0x40023D38	FULL	Master attributes 2
PERI_MS_PPU_FX212_MS_ATT3	0x40023D3C	FULL	Master attributes 3

21.230 PPU_FX 213

Register Name	Address	Permission	Description
PERI_MS_PPU_FX213_SL_ADDR	0x40023D40	FULL	Slave region, base address
PERI_MS_PPU_FX213_SL_SIZE	0x40023D44	FULL	Slave region, size
PERI_MS_PPU_FX213_SL_ATT0	0x40023D50	FULL	Slave attributes 0
PERI_MS_PPU_FX213_SL_ATT1	0x40023D54	FULL	Slave attributes 1
PERI_MS_PPU_FX213_SL_ATT2	0x40023D58	FULL	Slave attributes 2
PERI_MS_PPU_FX213_SL_ATT3	0x40023D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX213_MS_ADDR	0x40023D60	FULL	Master region, base address
PERI_MS_PPU_FX213_MS_SIZE	0x40023D64	FULL	Master region, size
PERI_MS_PPU_FX213_MS_ATT0	0x40023D70	FULL	Master attributes 0
PERI_MS_PPU_FX213_MS_ATT1	0x40023D74	FULL	Master attributes 1
PERI_MS_PPU_FX213_MS_ATT2	0x40023D78	FULL	Master attributes 2
PERI_MS_PPU_FX213_MS_ATT3	0x40023D7C	FULL	Master attributes 3

21.231 PPU_FX 214

Register Name	Address	Permission	Description
PERI_MS_PPU_FX214_SL_ADDR	0x40023D80	FULL	Slave region, base address
PERI_MS_PPU_FX214_SL_SIZE	0x40023D84	FULL	Slave region, size
PERI_MS_PPU_FX214_SL_ATT0	0x40023D90	FULL	Slave attributes 0
PERI_MS_PPU_FX214_SL_ATT1	0x40023D94	FULL	Slave attributes 1
PERI_MS_PPU_FX214_SL_ATT2	0x40023D98	FULL	Slave attributes 2
PERI_MS_PPU_FX214_SL_ATT3	0x40023D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX214_MS_ADDR	0x40023DA0	FULL	Master region, base address
PERI_MS_PPU_FX214_MS_SIZE	0x40023DA4	FULL	Master region, size
PERI_MS_PPU_FX214_MS_ATT0	0x40023DB0	FULL	Master attributes 0
PERI_MS_PPU_FX214_MS_ATT1	0x40023DB4	FULL	Master attributes 1
PERI_MS_PPU_FX214_MS_ATT2	0x40023DB8	FULL	Master attributes 2
PERI_MS_PPU_FX214_MS_ATT3	0x40023DBC	FULL	Master attributes 3

21.232 PPU_FX 215

Register Name	Address	Permission	Description
PERI_MS_PPU_FX215_SL_ADDR	0x40023DC0	FULL	Slave region, base address
PERI_MS_PPU_FX215_SL_SIZE	0x40023DC4	FULL	Slave region, size
PERI_MS_PPU_FX215_SL_ATT0	0x40023DD0	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX215_SL_ATT1	0x40023DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX215_SL_ATT2	0x40023DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX215_SL_ATT3	0x40023DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX215_MS_ADDR	0x40023DE0	FULL	Master region, base address
PERI_MS_PPU_FX215_MS_SIZE	0x40023DE4	FULL	Master region, size
PERI_MS_PPU_FX215_MS_ATT0	0x40023DF0	FULL	Master attributes 0
PERI_MS_PPU_FX215_MS_ATT1	0x40023DF4	FULL	Master attributes 1
PERI_MS_PPU_FX215_MS_ATT2	0x40023DF8	FULL	Master attributes 2
PERI_MS_PPU_FX215_MS_ATT3	0x40023DFC	FULL	Master attributes 3

21.233 PPU_FX 216

Register Name	Address	Permission	Description
PERI_MS_PPU_FX216_SL_ADDR	0x40023E00	FULL	Slave region, base address
PERI_MS_PPU_FX216_SL_SIZE	0x40023E04	FULL	Slave region, size
PERI_MS_PPU_FX216_SL_ATT0	0x40023E10	FULL	Slave attributes 0
PERI_MS_PPU_FX216_SL_ATT1	0x40023E14	FULL	Slave attributes 1
PERI_MS_PPU_FX216_SL_ATT2	0x40023E18	FULL	Slave attributes 2
PERI_MS_PPU_FX216_SL_ATT3	0x40023E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX216_MS_ADDR	0x40023E20	FULL	Master region, base address
PERI_MS_PPU_FX216_MS_SIZE	0x40023E24	FULL	Master region, size
PERI_MS_PPU_FX216_MS_ATT0	0x40023E30	FULL	Master attributes 0
PERI_MS_PPU_FX216_MS_ATT1	0x40023E34	FULL	Master attributes 1
PERI_MS_PPU_FX216_MS_ATT2	0x40023E38	FULL	Master attributes 2
PERI_MS_PPU_FX216_MS_ATT3	0x40023E3C	FULL	Master attributes 3

21.234 PPU_FX 217

Register Name	Address	Permission	Description
PERI_MS_PPU_FX217_SL_ADDR	0x40023E40	FULL	Slave region, base address
PERI_MS_PPU_FX217_SL_SIZE	0x40023E44	FULL	Slave region, size
PERI_MS_PPU_FX217_SL_ATT0	0x40023E50	FULL	Slave attributes 0
PERI_MS_PPU_FX217_SL_ATT1	0x40023E54	FULL	Slave attributes 1
PERI_MS_PPU_FX217_SL_ATT2	0x40023E58	FULL	Slave attributes 2
PERI_MS_PPU_FX217_SL_ATT3	0x40023E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX217_MS_ADDR	0x40023E60	FULL	Master region, base address
PERI_MS_PPU_FX217_MS_SIZE	0x40023E64	FULL	Master region, size
PERI_MS_PPU_FX217_MS_ATT0	0x40023E70	FULL	Master attributes 0
PERI_MS_PPU_FX217_MS_ATT1	0x40023E74	FULL	Master attributes 1
PERI_MS_PPU_FX217_MS_ATT2	0x40023E78	FULL	Master attributes 2
PERI_MS_PPU_FX217_MS_ATT3	0x40023E7C	FULL	Master attributes 3

21.235 PPU_FX 218

Register Name	Address	Permission	Description
PERI_MS_PPU_FX218_SL_ADDR	0x40023E80	FULL	Slave region, base address
PERI_MS_PPU_FX218_SL_SIZE	0x40023E84	FULL	Slave region, size
PERI_MS_PPU_FX218_SL_ATT0	0x40023E90	FULL	Slave attributes 0
PERI_MS_PPU_FX218_SL_ATT1	0x40023E94	FULL	Slave attributes 1
PERI_MS_PPU_FX218_SL_ATT2	0x40023E98	FULL	Slave attributes 2
PERI_MS_PPU_FX218_SL_ATT3	0x40023E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX218_MS_ADDR	0x40023EA0	FULL	Master region, base address
PERI_MS_PPU_FX218_MS_SIZE	0x40023EA4	FULL	Master region, size
PERI_MS_PPU_FX218_MS_ATT0	0x40023EB0	FULL	Master attributes 0
PERI_MS_PPU_FX218_MS_ATT1	0x40023EB4	FULL	Master attributes 1
PERI_MS_PPU_FX218_MS_ATT2	0x40023EB8	FULL	Master attributes 2
PERI_MS_PPU_FX218_MS_ATT3	0x40023EBC	FULL	Master attributes 3

21.236 PPU_FX 219

Register Name	Address	Permission	Description
PERI_MS_PPU_FX219_SL_ADDR	0x40023EC0	FULL	Slave region, base address
PERI_MS_PPU_FX219_SL_SIZE	0x40023EC4	FULL	Slave region, size
PERI_MS_PPU_FX219_SL_ATT0	0x40023ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX219_SL_ATT1	0x40023ED4	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX219_SL_ATT2	0x40023ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX219_SL_ATT3	0x40023EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX219_MS_ADDR	0x40023EE0	FULL	Master region, base address
PERI_MS_PPU_FX219_MS_SIZE	0x40023EE4	FULL	Master region, size
PERI_MS_PPU_FX219_MS_ATT0	0x40023EF0	FULL	Master attributes 0
PERI_MS_PPU_FX219_MS_ATT1	0x40023EF4	FULL	Master attributes 1
PERI_MS_PPU_FX219_MS_ATT2	0x40023EF8	FULL	Master attributes 2
PERI_MS_PPU_FX219_MS_ATT3	0x40023EFC	FULL	Master attributes 3

21.237 PPU_FX 220

Register Name	Address	Permission	Description
PERI_MS_PPU_FX220_SL_ADDR	0x40023F00	FULL	Slave region, base address
PERI_MS_PPU_FX220_SL_SIZE	0x40023F04	FULL	Slave region, size
PERI_MS_PPU_FX220_SL_ATT0	0x40023F10	FULL	Slave attributes 0
PERI_MS_PPU_FX220_SL_ATT1	0x40023F14	FULL	Slave attributes 1
PERI_MS_PPU_FX220_SL_ATT2	0x40023F18	FULL	Slave attributes 2
PERI_MS_PPU_FX220_SL_ATT3	0x40023F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX220_MS_ADDR	0x40023F20	FULL	Master region, base address
PERI_MS_PPU_FX220_MS_SIZE	0x40023F24	FULL	Master region, size
PERI_MS_PPU_FX220_MS_ATT0	0x40023F30	FULL	Master attributes 0
PERI_MS_PPU_FX220_MS_ATT1	0x40023F34	FULL	Master attributes 1
PERI_MS_PPU_FX220_MS_ATT2	0x40023F38	FULL	Master attributes 2
PERI_MS_PPU_FX220_MS_ATT3	0x40023F3C	FULL	Master attributes 3

21.238 PPU_FX 221

Register Name	Address	Permission	Description
PERI_MS_PPU_FX221_SL_ADDR	0x40023F40	FULL	Slave region, base address
PERI_MS_PPU_FX221_SL_SIZE	0x40023F44	FULL	Slave region, size
PERI_MS_PPU_FX221_SL_ATT0	0x40023F50	FULL	Slave attributes 0
PERI_MS_PPU_FX221_SL_ATT1	0x40023F54	FULL	Slave attributes 1
PERI_MS_PPU_FX221_SL_ATT2	0x40023F58	FULL	Slave attributes 2
PERI_MS_PPU_FX221_SL_ATT3	0x40023F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX221_MS_ADDR	0x40023F60	FULL	Master region, base address
PERI_MS_PPU_FX221_MS_SIZE	0x40023F64	FULL	Master region, size
PERI_MS_PPU_FX221_MS_ATT0	0x40023F70	FULL	Master attributes 0
PERI_MS_PPU_FX221_MS_ATT1	0x40023F74	FULL	Master attributes 1
PERI_MS_PPU_FX221_MS_ATT2	0x40023F78	FULL	Master attributes 2
PERI_MS_PPU_FX221_MS_ATT3	0x40023F7C	FULL	Master attributes 3

21.239 PPU_FX 222

Register Name	Address	Permission	Description
PERI_MS_PPU_FX222_SL_ADDR	0x40023F80	FULL	Slave region, base address
PERI_MS_PPU_FX222_SL_SIZE	0x40023F84	FULL	Slave region, size
PERI_MS_PPU_FX222_SL_ATT0	0x40023F90	FULL	Slave attributes 0
PERI_MS_PPU_FX222_SL_ATT1	0x40023F94	FULL	Slave attributes 1
PERI_MS_PPU_FX222_SL_ATT2	0x40023F98	FULL	Slave attributes 2
PERI_MS_PPU_FX222_SL_ATT3	0x40023F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX222_MS_ADDR	0x40023FA0	FULL	Master region, base address
PERI_MS_PPU_FX222_MS_SIZE	0x40023FA4	FULL	Master region, size
PERI_MS_PPU_FX222_MS_ATT0	0x40023FB0	FULL	Master attributes 0
PERI_MS_PPU_FX222_MS_ATT1	0x40023FB4	FULL	Master attributes 1
PERI_MS_PPU_FX222_MS_ATT2	0x40023FB8	FULL	Master attributes 2
PERI_MS_PPU_FX222_MS_ATT3	0x40023FBC	FULL	Master attributes 3

21.240 PPU_FX 223

Register Name	Address	Permission	Description
PERI_MS_PPU_FX223_SL_ADDR	0x40023FC0	FULL	Slave region, base address
PERI_MS_PPU_FX223_SL_SIZE	0x40023FC4	FULL	Slave region, size
PERI_MS_PPU_FX223_SL_ATT0	0x40023FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX223_SL_ATT1	0x40023FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX223_SL_ATT2	0x40023FD8	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX223_SL_ATT3	0x40023FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX223_MS_ADDR	0x40023FE0	FULL	Master region, base address
PERI_MS_PPU_FX223_MS_SIZE	0x40023FE4	FULL	Master region, size
PERI_MS_PPU_FX223_MS_ATT0	0x40023FF0	FULL	Master attributes 0
PERI_MS_PPU_FX223_MS_ATT1	0x40023FF4	FULL	Master attributes 1
PERI_MS_PPU_FX223_MS_ATT2	0x40023FF8	FULL	Master attributes 2
PERI_MS_PPU_FX223_MS_ATT3	0x40023FFC	FULL	Master attributes 3

21.241 PPU_FX 224

Register Name	Address	Permission	Description
PERI_MS_PPU_FX224_SL_ADDR	0x40024000	FULL	Slave region, base address
PERI_MS_PPU_FX224_SL_SIZE	0x40024004	FULL	Slave region, size
PERI_MS_PPU_FX224_SL_ATT0	0x40024010	FULL	Slave attributes 0
PERI_MS_PPU_FX224_SL_ATT1	0x40024014	FULL	Slave attributes 1
PERI_MS_PPU_FX224_SL_ATT2	0x40024018	FULL	Slave attributes 2
PERI_MS_PPU_FX224_SL_ATT3	0x4002401C	FULL	Slave attributes 3
PERI_MS_PPU_FX224_MS_ADDR	0x40024020	FULL	Master region, base address
PERI_MS_PPU_FX224_MS_SIZE	0x40024024	FULL	Master region, size
PERI_MS_PPU_FX224_MS_ATT0	0x40024030	FULL	Master attributes 0
PERI_MS_PPU_FX224_MS_ATT1	0x40024034	FULL	Master attributes 1
PERI_MS_PPU_FX224_MS_ATT2	0x40024038	FULL	Master attributes 2
PERI_MS_PPU_FX224_MS_ATT3	0x4002403C	FULL	Master attributes 3

21.242 PPU_FX 225

Register Name	Address	Permission	Description
PERI_MS_PPU_FX225_SL_ADDR	0x40024040	FULL	Slave region, base address
PERI_MS_PPU_FX225_SL_SIZE	0x40024044	FULL	Slave region, size
PERI_MS_PPU_FX225_SL_ATT0	0x40024050	FULL	Slave attributes 0
PERI_MS_PPU_FX225_SL_ATT1	0x40024054	FULL	Slave attributes 1
PERI_MS_PPU_FX225_SL_ATT2	0x40024058	FULL	Slave attributes 2
PERI_MS_PPU_FX225_SL_ATT3	0x4002405C	FULL	Slave attributes 3
PERI_MS_PPU_FX225_MS_ADDR	0x40024060	FULL	Master region, base address
PERI_MS_PPU_FX225_MS_SIZE	0x40024064	FULL	Master region, size
PERI_MS_PPU_FX225_MS_ATT0	0x40024070	FULL	Master attributes 0
PERI_MS_PPU_FX225_MS_ATT1	0x40024074	FULL	Master attributes 1
PERI_MS_PPU_FX225_MS_ATT2	0x40024078	FULL	Master attributes 2
PERI_MS_PPU_FX225_MS_ATT3	0x4002407C	FULL	Master attributes 3

21.243 PPU_FX 226

Register Name	Address	Permission	Description
PERI_MS_PPU_FX226_SL_ADDR	0x40024080	FULL	Slave region, base address
PERI_MS_PPU_FX226_SL_SIZE	0x40024084	FULL	Slave region, size
PERI_MS_PPU_FX226_SL_ATT0	0x40024090	FULL	Slave attributes 0
PERI_MS_PPU_FX226_SL_ATT1	0x40024094	FULL	Slave attributes 1
PERI_MS_PPU_FX226_SL_ATT2	0x40024098	FULL	Slave attributes 2
PERI_MS_PPU_FX226_SL_ATT3	0x4002409C	FULL	Slave attributes 3
PERI_MS_PPU_FX226_MS_ADDR	0x400240A0	FULL	Master region, base address
PERI_MS_PPU_FX226_MS_SIZE	0x400240A4	FULL	Master region, size
PERI_MS_PPU_FX226_MS_ATT0	0x400240B0	FULL	Master attributes 0
PERI_MS_PPU_FX226_MS_ATT1	0x400240B4	FULL	Master attributes 1
PERI_MS_PPU_FX226_MS_ATT2	0x400240B8	FULL	Master attributes 2
PERI_MS_PPU_FX226_MS_ATT3	0x400240BC	FULL	Master attributes 3

21.244 PPU_FX 227

Register Name	Address	Permission	Description
PERI_MS_PPU_FX227_SL_ADDR	0x400240C0	FULL	Slave region, base address
PERI_MS_PPU_FX227_SL_SIZE	0x400240C4	FULL	Slave region, size
PERI_MS_PPU_FX227_SL_ATT0	0x400240D0	FULL	Slave attributes 0
PERI_MS_PPU_FX227_SL_ATT1	0x400240D4	FULL	Slave attributes 1
PERI_MS_PPU_FX227_SL_ATT2	0x400240D8	FULL	Slave attributes 2
PERI_MS_PPU_FX227_SL_ATT3	0x400240DC	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX227_MS_ADDR	0x400240E0	FULL	Master region, base address
PERI_MS_PPU_FX227_MS_SIZE	0x400240E4	FULL	Master region, size
PERI_MS_PPU_FX227_MS_ATT0	0x400240F0	FULL	Master attributes 0
PERI_MS_PPU_FX227_MS_ATT1	0x400240F4	FULL	Master attributes 1
PERI_MS_PPU_FX227_MS_ATT2	0x400240F8	FULL	Master attributes 2
PERI_MS_PPU_FX227_MS_ATT3	0x400240FC	FULL	Master attributes 3

21.245 PPU_FX 228

Register Name	Address	Permission	Description
PERI_MS_PPU_FX228_SL_ADDR	0x40024100	FULL	Slave region, base address
PERI_MS_PPU_FX228_SL_SIZE	0x40024104	FULL	Slave region, size
PERI_MS_PPU_FX228_SL_ATT0	0x40024110	FULL	Slave attributes 0
PERI_MS_PPU_FX228_SL_ATT1	0x40024114	FULL	Slave attributes 1
PERI_MS_PPU_FX228_SL_ATT2	0x40024118	FULL	Slave attributes 2
PERI_MS_PPU_FX228_SL_ATT3	0x4002411C	FULL	Slave attributes 3
PERI_MS_PPU_FX228_MS_ADDR	0x40024120	FULL	Master region, base address
PERI_MS_PPU_FX228_MS_SIZE	0x40024124	FULL	Master region, size
PERI_MS_PPU_FX228_MS_ATT0	0x40024130	FULL	Master attributes 0
PERI_MS_PPU_FX228_MS_ATT1	0x40024134	FULL	Master attributes 1
PERI_MS_PPU_FX228_MS_ATT2	0x40024138	FULL	Master attributes 2
PERI_MS_PPU_FX228_MS_ATT3	0x4002413C	FULL	Master attributes 3

21.246 PPU_FX 229

Register Name	Address	Permission	Description
PERI_MS_PPU_FX229_SL_ADDR	0x40024140	FULL	Slave region, base address
PERI_MS_PPU_FX229_SL_SIZE	0x40024144	FULL	Slave region, size
PERI_MS_PPU_FX229_SL_ATT0	0x40024150	FULL	Slave attributes 0
PERI_MS_PPU_FX229_SL_ATT1	0x40024154	FULL	Slave attributes 1
PERI_MS_PPU_FX229_SL_ATT2	0x40024158	FULL	Slave attributes 2
PERI_MS_PPU_FX229_SL_ATT3	0x4002415C	FULL	Slave attributes 3
PERI_MS_PPU_FX229_MS_ADDR	0x40024160	FULL	Master region, base address
PERI_MS_PPU_FX229_MS_SIZE	0x40024164	FULL	Master region, size
PERI_MS_PPU_FX229_MS_ATT0	0x40024170	FULL	Master attributes 0
PERI_MS_PPU_FX229_MS_ATT1	0x40024174	FULL	Master attributes 1
PERI_MS_PPU_FX229_MS_ATT2	0x40024178	FULL	Master attributes 2
PERI_MS_PPU_FX229_MS_ATT3	0x4002417C	FULL	Master attributes 3

21.247 PPU_FX 230

Register Name	Address	Permission	Description
PERI_MS_PPU_FX230_SL_ADDR	0x40024180	FULL	Slave region, base address
PERI_MS_PPU_FX230_SL_SIZE	0x40024184	FULL	Slave region, size
PERI_MS_PPU_FX230_SL_ATT0	0x40024190	FULL	Slave attributes 0
PERI_MS_PPU_FX230_SL_ATT1	0x40024194	FULL	Slave attributes 1
PERI_MS_PPU_FX230_SL_ATT2	0x40024198	FULL	Slave attributes 2
PERI_MS_PPU_FX230_SL_ATT3	0x4002419C	FULL	Slave attributes 3
PERI_MS_PPU_FX230_MS_ADDR	0x400241A0	FULL	Master region, base address
PERI_MS_PPU_FX230_MS_SIZE	0x400241A4	FULL	Master region, size
PERI_MS_PPU_FX230_MS_ATT0	0x400241B0	FULL	Master attributes 0
PERI_MS_PPU_FX230_MS_ATT1	0x400241B4	FULL	Master attributes 1
PERI_MS_PPU_FX230_MS_ATT2	0x400241B8	FULL	Master attributes 2
PERI_MS_PPU_FX230_MS_ATT3	0x400241BC	FULL	Master attributes 3

21.248 PPU_FX 231

Register Name	Address	Permission	Description
PERI_MS_PPU_FX231_SL_ADDR	0x400241C0	FULL	Slave region, base address
PERI_MS_PPU_FX231_SL_SIZE	0x400241C4	FULL	Slave region, size
PERI_MS_PPU_FX231_SL_ATT0	0x400241D0	FULL	Slave attributes 0
PERI_MS_PPU_FX231_SL_ATT1	0x400241D4	FULL	Slave attributes 1
PERI_MS_PPU_FX231_SL_ATT2	0x400241D8	FULL	Slave attributes 2
PERI_MS_PPU_FX231_SL_ATT3	0x400241DC	FULL	Slave attributes 3
PERI_MS_PPU_FX231_MS_ADDR	0x400241E0	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX231_MS_SIZE	0x400241E4	FULL	Master region, size
PERI_MS_PPU_FX231_MS_ATT0	0x400241F0	FULL	Master attributes 0
PERI_MS_PPU_FX231_MS_ATT1	0x400241F4	FULL	Master attributes 1
PERI_MS_PPU_FX231_MS_ATT2	0x400241F8	FULL	Master attributes 2
PERI_MS_PPU_FX231_MS_ATT3	0x400241FC	FULL	Master attributes 3

21.249 PPU_FX 232

Register Name	Address	Permission	Description
PERI_MS_PPU_FX232_SL_ADDR	0x40024200	FULL	Slave region, base address
PERI_MS_PPU_FX232_SL_SIZE	0x40024204	FULL	Slave region, size
PERI_MS_PPU_FX232_SL_ATT0	0x40024210	FULL	Slave attributes 0
PERI_MS_PPU_FX232_SL_ATT1	0x40024214	FULL	Slave attributes 1
PERI_MS_PPU_FX232_SL_ATT2	0x40024218	FULL	Slave attributes 2
PERI_MS_PPU_FX232_SL_ATT3	0x4002421C	FULL	Slave attributes 3
PERI_MS_PPU_FX232_MS_ADDR	0x40024220	FULL	Master region, base address
PERI_MS_PPU_FX232_MS_SIZE	0x40024224	FULL	Master region, size
PERI_MS_PPU_FX232_MS_ATT0	0x40024230	FULL	Master attributes 0
PERI_MS_PPU_FX232_MS_ATT1	0x40024234	FULL	Master attributes 1
PERI_MS_PPU_FX232_MS_ATT2	0x40024238	FULL	Master attributes 2
PERI_MS_PPU_FX232_MS_ATT3	0x4002423C	FULL	Master attributes 3

21.250 PPU_FX 233

Register Name	Address	Permission	Description
PERI_MS_PPU_FX233_SL_ADDR	0x40024240	FULL	Slave region, base address
PERI_MS_PPU_FX233_SL_SIZE	0x40024244	FULL	Slave region, size
PERI_MS_PPU_FX233_SL_ATT0	0x40024250	FULL	Slave attributes 0
PERI_MS_PPU_FX233_SL_ATT1	0x40024254	FULL	Slave attributes 1
PERI_MS_PPU_FX233_SL_ATT2	0x40024258	FULL	Slave attributes 2
PERI_MS_PPU_FX233_SL_ATT3	0x4002425C	FULL	Slave attributes 3
PERI_MS_PPU_FX233_MS_ADDR	0x40024260	FULL	Master region, base address
PERI_MS_PPU_FX233_MS_SIZE	0x40024264	FULL	Master region, size
PERI_MS_PPU_FX233_MS_ATT0	0x40024270	FULL	Master attributes 0
PERI_MS_PPU_FX233_MS_ATT1	0x40024274	FULL	Master attributes 1
PERI_MS_PPU_FX233_MS_ATT2	0x40024278	FULL	Master attributes 2
PERI_MS_PPU_FX233_MS_ATT3	0x4002427C	FULL	Master attributes 3

21.251 PPU_FX 234

Register Name	Address	Permission	Description
PERI_MS_PPU_FX234_SL_ADDR	0x40024280	FULL	Slave region, base address
PERI_MS_PPU_FX234_SL_SIZE	0x40024284	FULL	Slave region, size
PERI_MS_PPU_FX234_SL_ATT0	0x40024290	FULL	Slave attributes 0
PERI_MS_PPU_FX234_SL_ATT1	0x40024294	FULL	Slave attributes 1
PERI_MS_PPU_FX234_SL_ATT2	0x40024298	FULL	Slave attributes 2
PERI_MS_PPU_FX234_SL_ATT3	0x4002429C	FULL	Slave attributes 3
PERI_MS_PPU_FX234_MS_ADDR	0x400242A0	FULL	Master region, base address
PERI_MS_PPU_FX234_MS_SIZE	0x400242A4	FULL	Master region, size
PERI_MS_PPU_FX234_MS_ATT0	0x400242B0	FULL	Master attributes 0
PERI_MS_PPU_FX234_MS_ATT1	0x400242B4	FULL	Master attributes 1
PERI_MS_PPU_FX234_MS_ATT2	0x400242B8	FULL	Master attributes 2
PERI_MS_PPU_FX234_MS_ATT3	0x400242BC	FULL	Master attributes 3

21.252 PPU_FX 235

Register Name	Address	Permission	Description
PERI_MS_PPU_FX235_SL_ADDR	0x400242C0	FULL	Slave region, base address
PERI_MS_PPU_FX235_SL_SIZE	0x400242C4	FULL	Slave region, size
PERI_MS_PPU_FX235_SL_ATT0	0x400242D0	FULL	Slave attributes 0
PERI_MS_PPU_FX235_SL_ATT1	0x400242D4	FULL	Slave attributes 1
PERI_MS_PPU_FX235_SL_ATT2	0x400242D8	FULL	Slave attributes 2
PERI_MS_PPU_FX235_SL_ATT3	0x400242DC	FULL	Slave attributes 3
PERI_MS_PPU_FX235_MS_ADDR	0x400242E0	FULL	Master region, base address
PERI_MS_PPU_FX235_MS_SIZE	0x400242E4	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX235_MS_ATT0	0x400242F0	FULL	Master attributes 0
PERI_MS_PPU_FX235_MS_ATT1	0x400242F4	FULL	Master attributes 1
PERI_MS_PPU_FX235_MS_ATT2	0x400242F8	FULL	Master attributes 2
PERI_MS_PPU_FX235_MS_ATT3	0x400242FC	FULL	Master attributes 3

21.253 PPU_FX 236

Register Name	Address	Permission	Description
PERI_MS_PPU_FX236_SL_ADDR	0x40024300	FULL	Slave region, base address
PERI_MS_PPU_FX236_SL_SIZE	0x40024304	FULL	Slave region, size
PERI_MS_PPU_FX236_SL_ATT0	0x40024310	FULL	Slave attributes 0
PERI_MS_PPU_FX236_SL_ATT1	0x40024314	FULL	Slave attributes 1
PERI_MS_PPU_FX236_SL_ATT2	0x40024318	FULL	Slave attributes 2
PERI_MS_PPU_FX236_SL_ATT3	0x4002431C	FULL	Slave attributes 3
PERI_MS_PPU_FX236_MS_ADDR	0x40024320	FULL	Master region, base address
PERI_MS_PPU_FX236_MS_SIZE	0x40024324	FULL	Master region, size
PERI_MS_PPU_FX236_MS_ATT0	0x40024330	FULL	Master attributes 0
PERI_MS_PPU_FX236_MS_ATT1	0x40024334	FULL	Master attributes 1
PERI_MS_PPU_FX236_MS_ATT2	0x40024338	FULL	Master attributes 2
PERI_MS_PPU_FX236_MS_ATT3	0x4002433C	FULL	Master attributes 3

21.254 PPU_FX 237

Register Name	Address	Permission	Description
PERI_MS_PPU_FX237_SL_ADDR	0x40024340	FULL	Slave region, base address
PERI_MS_PPU_FX237_SL_SIZE	0x40024344	FULL	Slave region, size
PERI_MS_PPU_FX237_SL_ATT0	0x40024350	FULL	Slave attributes 0
PERI_MS_PPU_FX237_SL_ATT1	0x40024354	FULL	Slave attributes 1
PERI_MS_PPU_FX237_SL_ATT2	0x40024358	FULL	Slave attributes 2
PERI_MS_PPU_FX237_SL_ATT3	0x4002435C	FULL	Slave attributes 3
PERI_MS_PPU_FX237_MS_ADDR	0x40024360	FULL	Master region, base address
PERI_MS_PPU_FX237_MS_SIZE	0x40024364	FULL	Master region, size
PERI_MS_PPU_FX237_MS_ATT0	0x40024370	FULL	Master attributes 0
PERI_MS_PPU_FX237_MS_ATT1	0x40024374	FULL	Master attributes 1
PERI_MS_PPU_FX237_MS_ATT2	0x40024378	FULL	Master attributes 2
PERI_MS_PPU_FX237_MS_ATT3	0x4002437C	FULL	Master attributes 3

21.255 PPU_FX 238

Register Name	Address	Permission	Description
PERI_MS_PPU_FX238_SL_ADDR	0x40024380	FULL	Slave region, base address
PERI_MS_PPU_FX238_SL_SIZE	0x40024384	FULL	Slave region, size
PERI_MS_PPU_FX238_SL_ATT0	0x40024390	FULL	Slave attributes 0
PERI_MS_PPU_FX238_SL_ATT1	0x40024394	FULL	Slave attributes 1
PERI_MS_PPU_FX238_SL_ATT2	0x40024398	FULL	Slave attributes 2
PERI_MS_PPU_FX238_SL_ATT3	0x4002439C	FULL	Slave attributes 3
PERI_MS_PPU_FX238_MS_ADDR	0x400243A0	FULL	Master region, base address
PERI_MS_PPU_FX238_MS_SIZE	0x400243A4	FULL	Master region, size
PERI_MS_PPU_FX238_MS_ATT0	0x400243B0	FULL	Master attributes 0
PERI_MS_PPU_FX238_MS_ATT1	0x400243B4	FULL	Master attributes 1
PERI_MS_PPU_FX238_MS_ATT2	0x400243B8	FULL	Master attributes 2
PERI_MS_PPU_FX238_MS_ATT3	0x400243BC	FULL	Master attributes 3

21.256 PPU_FX 239

Register Name	Address	Permission	Description
PERI_MS_PPU_FX239_SL_ADDR	0x400243C0	FULL	Slave region, base address
PERI_MS_PPU_FX239_SL_SIZE	0x400243C4	FULL	Slave region, size
PERI_MS_PPU_FX239_SL_ATT0	0x400243D0	FULL	Slave attributes 0
PERI_MS_PPU_FX239_SL_ATT1	0x400243D4	FULL	Slave attributes 1
PERI_MS_PPU_FX239_SL_ATT2	0x400243D8	FULL	Slave attributes 2
PERI_MS_PPU_FX239_SL_ATT3	0x400243DC	FULL	Slave attributes 3
PERI_MS_PPU_FX239_MS_ADDR	0x400243E0	FULL	Master region, base address
PERI_MS_PPU_FX239_MS_SIZE	0x400243E4	FULL	Master region, size
PERI_MS_PPU_FX239_MS_ATT0	0x400243F0	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX239_MS_ATT1	0x400243F4	FULL	Master attributes 1
PERI_MS_PPU_FX239_MS_ATT2	0x400243F8	FULL	Master attributes 2
PERI_MS_PPU_FX239_MS_ATT3	0x400243FC	FULL	Master attributes 3

21.257 PPU_FX 240

Register Name	Address	Permission	Description
PERI_MS_PPU_FX240_SL_ADDR	0x40024400	FULL	Slave region, base address
PERI_MS_PPU_FX240_SL_SIZE	0x40024404	FULL	Slave region, size
PERI_MS_PPU_FX240_SL_ATT0	0x40024410	FULL	Slave attributes 0
PERI_MS_PPU_FX240_SL_ATT1	0x40024414	FULL	Slave attributes 1
PERI_MS_PPU_FX240_SL_ATT2	0x40024418	FULL	Slave attributes 2
PERI_MS_PPU_FX240_SL_ATT3	0x4002441C	FULL	Slave attributes 3
PERI_MS_PPU_FX240_MS_ADDR	0x40024420	FULL	Master region, base address
PERI_MS_PPU_FX240_MS_SIZE	0x40024424	FULL	Master region, size
PERI_MS_PPU_FX240_MS_ATT0	0x40024430	FULL	Master attributes 0
PERI_MS_PPU_FX240_MS_ATT1	0x40024434	FULL	Master attributes 1
PERI_MS_PPU_FX240_MS_ATT2	0x40024438	FULL	Master attributes 2
PERI_MS_PPU_FX240_MS_ATT3	0x4002443C	FULL	Master attributes 3

21.258 PPU_FX 241

Register Name	Address	Permission	Description
PERI_MS_PPU_FX241_SL_ADDR	0x40024440	FULL	Slave region, base address
PERI_MS_PPU_FX241_SL_SIZE	0x40024444	FULL	Slave region, size
PERI_MS_PPU_FX241_SL_ATT0	0x40024450	FULL	Slave attributes 0
PERI_MS_PPU_FX241_SL_ATT1	0x40024454	FULL	Slave attributes 1
PERI_MS_PPU_FX241_SL_ATT2	0x40024458	FULL	Slave attributes 2
PERI_MS_PPU_FX241_SL_ATT3	0x4002445C	FULL	Slave attributes 3
PERI_MS_PPU_FX241_MS_ADDR	0x40024460	FULL	Master region, base address
PERI_MS_PPU_FX241_MS_SIZE	0x40024464	FULL	Master region, size
PERI_MS_PPU_FX241_MS_ATT0	0x40024470	FULL	Master attributes 0
PERI_MS_PPU_FX241_MS_ATT1	0x40024474	FULL	Master attributes 1
PERI_MS_PPU_FX241_MS_ATT2	0x40024478	FULL	Master attributes 2
PERI_MS_PPU_FX241_MS_ATT3	0x4002447C	FULL	Master attributes 3

21.259 PPU_FX 242

Register Name	Address	Permission	Description
PERI_MS_PPU_FX242_SL_ADDR	0x40024480	FULL	Slave region, base address
PERI_MS_PPU_FX242_SL_SIZE	0x40024484	FULL	Slave region, size
PERI_MS_PPU_FX242_SL_ATT0	0x40024490	FULL	Slave attributes 0
PERI_MS_PPU_FX242_SL_ATT1	0x40024494	FULL	Slave attributes 1
PERI_MS_PPU_FX242_SL_ATT2	0x40024498	FULL	Slave attributes 2
PERI_MS_PPU_FX242_SL_ATT3	0x4002449C	FULL	Slave attributes 3
PERI_MS_PPU_FX242_MS_ADDR	0x400244A0	FULL	Master region, base address
PERI_MS_PPU_FX242_MS_SIZE	0x400244A4	FULL	Master region, size
PERI_MS_PPU_FX242_MS_ATT0	0x400244B0	FULL	Master attributes 0
PERI_MS_PPU_FX242_MS_ATT1	0x400244B4	FULL	Master attributes 1
PERI_MS_PPU_FX242_MS_ATT2	0x400244B8	FULL	Master attributes 2
PERI_MS_PPU_FX242_MS_ATT3	0x400244BC	FULL	Master attributes 3

21.260 PPU_FX 243

Register Name	Address	Permission	Description
PERI_MS_PPU_FX243_SL_ADDR	0x400244C0	FULL	Slave region, base address
PERI_MS_PPU_FX243_SL_SIZE	0x400244C4	FULL	Slave region, size
PERI_MS_PPU_FX243_SL_ATT0	0x400244D0	FULL	Slave attributes 0
PERI_MS_PPU_FX243_SL_ATT1	0x400244D4	FULL	Slave attributes 1
PERI_MS_PPU_FX243_SL_ATT2	0x400244D8	FULL	Slave attributes 2
PERI_MS_PPU_FX243_SL_ATT3	0x400244DC	FULL	Slave attributes 3
PERI_MS_PPU_FX243_MS_ADDR	0x400244E0	FULL	Master region, base address
PERI_MS_PPU_FX243_MS_SIZE	0x400244E4	FULL	Master region, size
PERI_MS_PPU_FX243_MS_ATT0	0x400244F0	FULL	Master attributes 0
PERI_MS_PPU_FX243_MS_ATT1	0x400244F4	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX243_MS_ATT2	0x400244F8	FULL	Master attributes 2
PERI_MS_PPU_FX243_MS_ATT3	0x400244FC	FULL	Master attributes 3

21.261 PPU_FX 244

Register Name	Address	Permission	Description
PERI_MS_PPU_FX244_SL_ADDR	0x40024500	FULL	Slave region, base address
PERI_MS_PPU_FX244_SL_SIZE	0x40024504	FULL	Slave region, size
PERI_MS_PPU_FX244_SL_ATT0	0x40024510	FULL	Slave attributes 0
PERI_MS_PPU_FX244_SL_ATT1	0x40024514	FULL	Slave attributes 1
PERI_MS_PPU_FX244_SL_ATT2	0x40024518	FULL	Slave attributes 2
PERI_MS_PPU_FX244_SL_ATT3	0x4002451C	FULL	Slave attributes 3
PERI_MS_PPU_FX244_MS_ADDR	0x40024520	FULL	Master region, base address
PERI_MS_PPU_FX244_MS_SIZE	0x40024524	FULL	Master region, size
PERI_MS_PPU_FX244_MS_ATT0	0x40024530	FULL	Master attributes 0
PERI_MS_PPU_FX244_MS_ATT1	0x40024534	FULL	Master attributes 1
PERI_MS_PPU_FX244_MS_ATT2	0x40024538	FULL	Master attributes 2
PERI_MS_PPU_FX244_MS_ATT3	0x4002453C	FULL	Master attributes 3

21.262 PPU_FX 245

Register Name	Address	Permission	Description
PERI_MS_PPU_FX245_SL_ADDR	0x40024540	FULL	Slave region, base address
PERI_MS_PPU_FX245_SL_SIZE	0x40024544	FULL	Slave region, size
PERI_MS_PPU_FX245_SL_ATT0	0x40024550	FULL	Slave attributes 0
PERI_MS_PPU_FX245_SL_ATT1	0x40024554	FULL	Slave attributes 1
PERI_MS_PPU_FX245_SL_ATT2	0x40024558	FULL	Slave attributes 2
PERI_MS_PPU_FX245_SL_ATT3	0x4002455C	FULL	Slave attributes 3
PERI_MS_PPU_FX245_MS_ADDR	0x40024560	FULL	Master region, base address
PERI_MS_PPU_FX245_MS_SIZE	0x40024564	FULL	Master region, size
PERI_MS_PPU_FX245_MS_ATT0	0x40024570	FULL	Master attributes 0
PERI_MS_PPU_FX245_MS_ATT1	0x40024574	FULL	Master attributes 1
PERI_MS_PPU_FX245_MS_ATT2	0x40024578	FULL	Master attributes 2
PERI_MS_PPU_FX245_MS_ATT3	0x4002457C	FULL	Master attributes 3

21.263 PPU_FX 246

Register Name	Address	Permission	Description
PERI_MS_PPU_FX246_SL_ADDR	0x40024580	FULL	Slave region, base address
PERI_MS_PPU_FX246_SL_SIZE	0x40024584	FULL	Slave region, size
PERI_MS_PPU_FX246_SL_ATT0	0x40024590	FULL	Slave attributes 0
PERI_MS_PPU_FX246_SL_ATT1	0x40024594	FULL	Slave attributes 1
PERI_MS_PPU_FX246_SL_ATT2	0x40024598	FULL	Slave attributes 2
PERI_MS_PPU_FX246_SL_ATT3	0x4002459C	FULL	Slave attributes 3
PERI_MS_PPU_FX246_MS_ADDR	0x400245A0	FULL	Master region, base address
PERI_MS_PPU_FX246_MS_SIZE	0x400245A4	FULL	Master region, size
PERI_MS_PPU_FX246_MS_ATT0	0x400245B0	FULL	Master attributes 0
PERI_MS_PPU_FX246_MS_ATT1	0x400245B4	FULL	Master attributes 1
PERI_MS_PPU_FX246_MS_ATT2	0x400245B8	FULL	Master attributes 2
PERI_MS_PPU_FX246_MS_ATT3	0x400245BC	FULL	Master attributes 3

21.264 PPU_FX 247

Register Name	Address	Permission	Description
PERI_MS_PPU_FX247_SL_ADDR	0x400245C0	FULL	Slave region, base address
PERI_MS_PPU_FX247_SL_SIZE	0x400245C4	FULL	Slave region, size
PERI_MS_PPU_FX247_SL_ATT0	0x400245D0	FULL	Slave attributes 0
PERI_MS_PPU_FX247_SL_ATT1	0x400245D4	FULL	Slave attributes 1
PERI_MS_PPU_FX247_SL_ATT2	0x400245D8	FULL	Slave attributes 2
PERI_MS_PPU_FX247_SL_ATT3	0x400245DC	FULL	Slave attributes 3
PERI_MS_PPU_FX247_MS_ADDR	0x400245E0	FULL	Master region, base address
PERI_MS_PPU_FX247_MS_SIZE	0x400245E4	FULL	Master region, size
PERI_MS_PPU_FX247_MS_ATT0	0x400245F0	FULL	Master attributes 0
PERI_MS_PPU_FX247_MS_ATT1	0x400245F4	FULL	Master attributes 1
PERI_MS_PPU_FX247_MS_ATT2	0x400245F8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX247_MS_ATT3	0x400245FC	FULL	Master attributes 3

21.265 PPU_FX 248

Register Name	Address	Permission	Description
PERI_MS_PPU_FX248_SL_ADDR	0x40024600	FULL	Slave region, base address
PERI_MS_PPU_FX248_SL_SIZE	0x40024604	FULL	Slave region, size
PERI_MS_PPU_FX248_SL_ATT0	0x40024610	FULL	Slave attributes 0
PERI_MS_PPU_FX248_SL_ATT1	0x40024614	FULL	Slave attributes 1
PERI_MS_PPU_FX248_SL_ATT2	0x40024618	FULL	Slave attributes 2
PERI_MS_PPU_FX248_SL_ATT3	0x4002461C	FULL	Slave attributes 3
PERI_MS_PPU_FX248_MS_ADDR	0x40024620	FULL	Master region, base address
PERI_MS_PPU_FX248_MS_SIZE	0x40024624	FULL	Master region, size
PERI_MS_PPU_FX248_MS_ATT0	0x40024630	FULL	Master attributes 0
PERI_MS_PPU_FX248_MS_ATT1	0x40024634	FULL	Master attributes 1
PERI_MS_PPU_FX248_MS_ATT2	0x40024638	FULL	Master attributes 2
PERI_MS_PPU_FX248_MS_ATT3	0x4002463C	FULL	Master attributes 3

21.266 PPU_FX 249

Register Name	Address	Permission	Description
PERI_MS_PPU_FX249_SL_ADDR	0x40024640	FULL	Slave region, base address
PERI_MS_PPU_FX249_SL_SIZE	0x40024644	FULL	Slave region, size
PERI_MS_PPU_FX249_SL_ATT0	0x40024650	FULL	Slave attributes 0
PERI_MS_PPU_FX249_SL_ATT1	0x40024654	FULL	Slave attributes 1
PERI_MS_PPU_FX249_SL_ATT2	0x40024658	FULL	Slave attributes 2
PERI_MS_PPU_FX249_SL_ATT3	0x4002465C	FULL	Slave attributes 3
PERI_MS_PPU_FX249_MS_ADDR	0x40024660	FULL	Master region, base address
PERI_MS_PPU_FX249_MS_SIZE	0x40024664	FULL	Master region, size
PERI_MS_PPU_FX249_MS_ATT0	0x40024670	FULL	Master attributes 0
PERI_MS_PPU_FX249_MS_ATT1	0x40024674	FULL	Master attributes 1
PERI_MS_PPU_FX249_MS_ATT2	0x40024678	FULL	Master attributes 2
PERI_MS_PPU_FX249_MS_ATT3	0x4002467C	FULL	Master attributes 3

21.267 PPU_FX 250

Register Name	Address	Permission	Description
PERI_MS_PPU_FX250_SL_ADDR	0x40024680	FULL	Slave region, base address
PERI_MS_PPU_FX250_SL_SIZE	0x40024684	FULL	Slave region, size
PERI_MS_PPU_FX250_SL_ATT0	0x40024690	FULL	Slave attributes 0
PERI_MS_PPU_FX250_SL_ATT1	0x40024694	FULL	Slave attributes 1
PERI_MS_PPU_FX250_SL_ATT2	0x40024698	FULL	Slave attributes 2
PERI_MS_PPU_FX250_SL_ATT3	0x4002469C	FULL	Slave attributes 3
PERI_MS_PPU_FX250_MS_ADDR	0x400246A0	FULL	Master region, base address
PERI_MS_PPU_FX250_MS_SIZE	0x400246A4	FULL	Master region, size
PERI_MS_PPU_FX250_MS_ATT0	0x400246B0	FULL	Master attributes 0
PERI_MS_PPU_FX250_MS_ATT1	0x400246B4	FULL	Master attributes 1
PERI_MS_PPU_FX250_MS_ATT2	0x400246B8	FULL	Master attributes 2
PERI_MS_PPU_FX250_MS_ATT3	0x400246BC	FULL	Master attributes 3

21.268 PPU_FX 251

Register Name	Address	Permission	Description
PERI_MS_PPU_FX251_SL_ADDR	0x400246C0	FULL	Slave region, base address
PERI_MS_PPU_FX251_SL_SIZE	0x400246C4	FULL	Slave region, size
PERI_MS_PPU_FX251_SL_ATT0	0x400246D0	FULL	Slave attributes 0
PERI_MS_PPU_FX251_SL_ATT1	0x400246D4	FULL	Slave attributes 1
PERI_MS_PPU_FX251_SL_ATT2	0x400246D8	FULL	Slave attributes 2
PERI_MS_PPU_FX251_SL_ATT3	0x400246DC	FULL	Slave attributes 3
PERI_MS_PPU_FX251_MS_ADDR	0x400246E0	FULL	Master region, base address
PERI_MS_PPU_FX251_MS_SIZE	0x400246E4	FULL	Master region, size
PERI_MS_PPU_FX251_MS_ATT0	0x400246F0	FULL	Master attributes 0
PERI_MS_PPU_FX251_MS_ATT1	0x400246F4	FULL	Master attributes 1
PERI_MS_PPU_FX251_MS_ATT2	0x400246F8	FULL	Master attributes 2
PERI_MS_PPU_FX251_MS_ATT3	0x400246FC	FULL	Master attributes 3

21.269 PPU_FX 252

Register Name	Address	Permission	Description
PERI_MS_PPU_FX252_SL_ADDR	0x40024700	FULL	Slave region, base address
PERI_MS_PPU_FX252_SL_SIZE	0x40024704	FULL	Slave region, size
PERI_MS_PPU_FX252_SL_ATT0	0x40024710	FULL	Slave attributes 0
PERI_MS_PPU_FX252_SL_ATT1	0x40024714	FULL	Slave attributes 1
PERI_MS_PPU_FX252_SL_ATT2	0x40024718	FULL	Slave attributes 2
PERI_MS_PPU_FX252_SL_ATT3	0x4002471C	FULL	Slave attributes 3
PERI_MS_PPU_FX252_MS_ADDR	0x40024720	FULL	Master region, base address
PERI_MS_PPU_FX252_MS_SIZE	0x40024724	FULL	Master region, size
PERI_MS_PPU_FX252_MS_ATT0	0x40024730	FULL	Master attributes 0
PERI_MS_PPU_FX252_MS_ATT1	0x40024734	FULL	Master attributes 1
PERI_MS_PPU_FX252_MS_ATT2	0x40024738	FULL	Master attributes 2
PERI_MS_PPU_FX252_MS_ATT3	0x4002473C	FULL	Master attributes 3

21.270 PPU_FX 253

Register Name	Address	Permission	Description
PERI_MS_PPU_FX253_SL_ADDR	0x40024740	FULL	Slave region, base address
PERI_MS_PPU_FX253_SL_SIZE	0x40024744	FULL	Slave region, size
PERI_MS_PPU_FX253_SL_ATT0	0x40024750	FULL	Slave attributes 0
PERI_MS_PPU_FX253_SL_ATT1	0x40024754	FULL	Slave attributes 1
PERI_MS_PPU_FX253_SL_ATT2	0x40024758	FULL	Slave attributes 2
PERI_MS_PPU_FX253_SL_ATT3	0x4002475C	FULL	Slave attributes 3
PERI_MS_PPU_FX253_MS_ADDR	0x40024760	FULL	Master region, base address
PERI_MS_PPU_FX253_MS_SIZE	0x40024764	FULL	Master region, size
PERI_MS_PPU_FX253_MS_ATT0	0x40024770	FULL	Master attributes 0
PERI_MS_PPU_FX253_MS_ATT1	0x40024774	FULL	Master attributes 1
PERI_MS_PPU_FX253_MS_ATT2	0x40024778	FULL	Master attributes 2
PERI_MS_PPU_FX253_MS_ATT3	0x4002477C	FULL	Master attributes 3

21.271 PPU_FX 254

Register Name	Address	Permission	Description
PERI_MS_PPU_FX254_SL_ADDR	0x40024780	FULL	Slave region, base address
PERI_MS_PPU_FX254_SL_SIZE	0x40024784	FULL	Slave region, size
PERI_MS_PPU_FX254_SL_ATT0	0x40024790	FULL	Slave attributes 0
PERI_MS_PPU_FX254_SL_ATT1	0x40024794	FULL	Slave attributes 1
PERI_MS_PPU_FX254_SL_ATT2	0x40024798	FULL	Slave attributes 2
PERI_MS_PPU_FX254_SL_ATT3	0x4002479C	FULL	Slave attributes 3
PERI_MS_PPU_FX254_MS_ADDR	0x400247A0	FULL	Master region, base address
PERI_MS_PPU_FX254_MS_SIZE	0x400247A4	FULL	Master region, size
PERI_MS_PPU_FX254_MS_ATT0	0x400247B0	FULL	Master attributes 0
PERI_MS_PPU_FX254_MS_ATT1	0x400247B4	FULL	Master attributes 1
PERI_MS_PPU_FX254_MS_ATT2	0x400247B8	FULL	Master attributes 2
PERI_MS_PPU_FX254_MS_ATT3	0x400247BC	FULL	Master attributes 3

21.272 PPU_FX 255

Register Name	Address	Permission	Description
PERI_MS_PPU_FX255_SL_ADDR	0x400247C0	FULL	Slave region, base address
PERI_MS_PPU_FX255_SL_SIZE	0x400247C4	FULL	Slave region, size
PERI_MS_PPU_FX255_SL_ATT0	0x400247D0	FULL	Slave attributes 0
PERI_MS_PPU_FX255_SL_ATT1	0x400247D4	FULL	Slave attributes 1
PERI_MS_PPU_FX255_SL_ATT2	0x400247D8	FULL	Slave attributes 2
PERI_MS_PPU_FX255_SL_ATT3	0x400247DC	FULL	Slave attributes 3
PERI_MS_PPU_FX255_MS_ADDR	0x400247E0	FULL	Master region, base address
PERI_MS_PPU_FX255_MS_SIZE	0x400247E4	FULL	Master region, size
PERI_MS_PPU_FX255_MS_ATT0	0x400247F0	FULL	Master attributes 0
PERI_MS_PPU_FX255_MS_ATT1	0x400247F4	FULL	Master attributes 1
PERI_MS_PPU_FX255_MS_ATT2	0x400247F8	FULL	Master attributes 2
PERI_MS_PPU_FX255_MS_ATT3	0x400247FC	FULL	Master attributes 3

21.273 PPU_FX 256

Register Name	Address	Permission	Description
PERI_MS_PPU_FX256_SL_ADDR	0x40024800	FULL	Slave region, base address
PERI_MS_PPU_FX256_SL_SIZE	0x40024804	FULL	Slave region, size
PERI_MS_PPU_FX256_SL_ATT0	0x40024810	FULL	Slave attributes 0
PERI_MS_PPU_FX256_SL_ATT1	0x40024814	FULL	Slave attributes 1
PERI_MS_PPU_FX256_SL_ATT2	0x40024818	FULL	Slave attributes 2
PERI_MS_PPU_FX256_SL_ATT3	0x4002481C	FULL	Slave attributes 3
PERI_MS_PPU_FX256_MS_ADDR	0x40024820	FULL	Master region, base address
PERI_MS_PPU_FX256_MS_SIZE	0x40024824	FULL	Master region, size
PERI_MS_PPU_FX256_MS_ATT0	0x40024830	FULL	Master attributes 0
PERI_MS_PPU_FX256_MS_ATT1	0x40024834	FULL	Master attributes 1
PERI_MS_PPU_FX256_MS_ATT2	0x40024838	FULL	Master attributes 2
PERI_MS_PPU_FX256_MS_ATT3	0x4002483C	FULL	Master attributes 3

21.274 PPU_FX 257

Register Name	Address	Permission	Description
PERI_MS_PPU_FX257_SL_ADDR	0x40024840	FULL	Slave region, base address
PERI_MS_PPU_FX257_SL_SIZE	0x40024844	FULL	Slave region, size
PERI_MS_PPU_FX257_SL_ATT0	0x40024850	FULL	Slave attributes 0
PERI_MS_PPU_FX257_SL_ATT1	0x40024854	FULL	Slave attributes 1
PERI_MS_PPU_FX257_SL_ATT2	0x40024858	FULL	Slave attributes 2
PERI_MS_PPU_FX257_SL_ATT3	0x4002485C	FULL	Slave attributes 3
PERI_MS_PPU_FX257_MS_ADDR	0x40024860	FULL	Master region, base address
PERI_MS_PPU_FX257_MS_SIZE	0x40024864	FULL	Master region, size
PERI_MS_PPU_FX257_MS_ATT0	0x40024870	FULL	Master attributes 0
PERI_MS_PPU_FX257_MS_ATT1	0x40024874	FULL	Master attributes 1
PERI_MS_PPU_FX257_MS_ATT2	0x40024878	FULL	Master attributes 2
PERI_MS_PPU_FX257_MS_ATT3	0x4002487C	FULL	Master attributes 3

21.275 PPU_FX 258

Register Name	Address	Permission	Description
PERI_MS_PPU_FX258_SL_ADDR	0x40024880	FULL	Slave region, base address
PERI_MS_PPU_FX258_SL_SIZE	0x40024884	FULL	Slave region, size
PERI_MS_PPU_FX258_SL_ATT0	0x40024890	FULL	Slave attributes 0
PERI_MS_PPU_FX258_SL_ATT1	0x40024894	FULL	Slave attributes 1
PERI_MS_PPU_FX258_SL_ATT2	0x40024898	FULL	Slave attributes 2
PERI_MS_PPU_FX258_SL_ATT3	0x4002489C	FULL	Slave attributes 3
PERI_MS_PPU_FX258_MS_ADDR	0x400248A0	FULL	Master region, base address
PERI_MS_PPU_FX258_MS_SIZE	0x400248A4	FULL	Master region, size
PERI_MS_PPU_FX258_MS_ATT0	0x400248B0	FULL	Master attributes 0
PERI_MS_PPU_FX258_MS_ATT1	0x400248B4	FULL	Master attributes 1
PERI_MS_PPU_FX258_MS_ATT2	0x400248B8	FULL	Master attributes 2
PERI_MS_PPU_FX258_MS_ATT3	0x400248BC	FULL	Master attributes 3

21.276 PPU_FX 259

Register Name	Address	Permission	Description
PERI_MS_PPU_FX259_SL_ADDR	0x400248C0	FULL	Slave region, base address
PERI_MS_PPU_FX259_SL_SIZE	0x400248C4	FULL	Slave region, size
PERI_MS_PPU_FX259_SL_ATT0	0x400248D0	FULL	Slave attributes 0
PERI_MS_PPU_FX259_SL_ATT1	0x400248D4	FULL	Slave attributes 1
PERI_MS_PPU_FX259_SL_ATT2	0x400248D8	FULL	Slave attributes 2
PERI_MS_PPU_FX259_SL_ATT3	0x400248DC	FULL	Slave attributes 3
PERI_MS_PPU_FX259_MS_ADDR	0x400248E0	FULL	Master region, base address
PERI_MS_PPU_FX259_MS_SIZE	0x400248E4	FULL	Master region, size
PERI_MS_PPU_FX259_MS_ATT0	0x400248F0	FULL	Master attributes 0
PERI_MS_PPU_FX259_MS_ATT1	0x400248F4	FULL	Master attributes 1
PERI_MS_PPU_FX259_MS_ATT2	0x400248F8	FULL	Master attributes 2
PERI_MS_PPU_FX259_MS_ATT3	0x400248FC	FULL	Master attributes 3

21.277 PPU_FX 260

Register Name	Address	Permission	Description
PERI_MS_PPU_FX260_SL_ADDR	0x40024900	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX260_SL_SIZE	0x40024904	FULL	Slave region, size
PERI_MS_PPU_FX260_SL_ATT0	0x40024910	FULL	Slave attributes 0
PERI_MS_PPU_FX260_SL_ATT1	0x40024914	FULL	Slave attributes 1
PERI_MS_PPU_FX260_SL_ATT2	0x40024918	FULL	Slave attributes 2
PERI_MS_PPU_FX260_SL_ATT3	0x4002491C	FULL	Slave attributes 3
PERI_MS_PPU_FX260_MS_ADDR	0x40024920	FULL	Master region, base address
PERI_MS_PPU_FX260_MS_SIZE	0x40024924	FULL	Master region, size
PERI_MS_PPU_FX260_MS_ATT0	0x40024930	FULL	Master attributes 0
PERI_MS_PPU_FX260_MS_ATT1	0x40024934	FULL	Master attributes 1
PERI_MS_PPU_FX260_MS_ATT2	0x40024938	FULL	Master attributes 2
PERI_MS_PPU_FX260_MS_ATT3	0x4002493C	FULL	Master attributes 3

21.278 PPU_FX 261

Register Name	Address	Permission	Description
PERI_MS_PPU_FX261_SL_ADDR	0x40024940	READ	Slave region, base address
PERI_MS_PPU_FX261_SL_SIZE	0x40024944	READ	Slave region, size
PERI_MS_PPU_FX261_SL_ATT0	0x40024950	READ	Slave attributes 0
PERI_MS_PPU_FX261_SL_ATT1	0x40024954	READ	Slave attributes 1
PERI_MS_PPU_FX261_SL_ATT2	0x40024958	READ	Slave attributes 2
PERI_MS_PPU_FX261_SL_ATT3	0x4002495C	READ	Slave attributes 3
PERI_MS_PPU_FX261_MS_ADDR	0x40024960	READ	Master region, base address
PERI_MS_PPU_FX261_MS_SIZE	0x40024964	READ	Master region, size
PERI_MS_PPU_FX261_MS_ATT0	0x40024970	READ	Master attributes 0
PERI_MS_PPU_FX261_MS_ATT1	0x40024974	READ	Master attributes 1
PERI_MS_PPU_FX261_MS_ATT2	0x40024978	READ	Master attributes 2
PERI_MS_PPU_FX261_MS_ATT3	0x4002497C	READ	Master attributes 3

21.279 PPU_FX 262

Register Name	Address	Permission	Description
PERI_MS_PPU_FX262_SL_ADDR	0x40024980	READ	Slave region, base address
PERI_MS_PPU_FX262_SL_SIZE	0x40024984	READ	Slave region, size
PERI_MS_PPU_FX262_SL_ATT0	0x40024990	READ	Slave attributes 0
PERI_MS_PPU_FX262_SL_ATT1	0x40024994	READ	Slave attributes 1
PERI_MS_PPU_FX262_SL_ATT2	0x40024998	READ	Slave attributes 2
PERI_MS_PPU_FX262_SL_ATT3	0x4002499C	READ	Slave attributes 3
PERI_MS_PPU_FX262_MS_ADDR	0x400249A0	READ	Master region, base address
PERI_MS_PPU_FX262_MS_SIZE	0x400249A4	READ	Master region, size
PERI_MS_PPU_FX262_MS_ATT0	0x400249B0	READ	Master attributes 0
PERI_MS_PPU_FX262_MS_ATT1	0x400249B4	READ	Master attributes 1
PERI_MS_PPU_FX262_MS_ATT2	0x400249B8	READ	Master attributes 2
PERI_MS_PPU_FX262_MS_ATT3	0x400249BC	READ	Master attributes 3

21.280 PPU_FX 263

Register Name	Address	Permission	Description
PERI_MS_PPU_FX263_SL_ADDR	0x400249C0	READ	Slave region, base address
PERI_MS_PPU_FX263_SL_SIZE	0x400249C4	READ	Slave region, size
PERI_MS_PPU_FX263_SL_ATT0	0x400249D0	READ	Slave attributes 0
PERI_MS_PPU_FX263_SL_ATT1	0x400249D4	READ	Slave attributes 1
PERI_MS_PPU_FX263_SL_ATT2	0x400249D8	READ	Slave attributes 2
PERI_MS_PPU_FX263_SL_ATT3	0x400249DC	READ	Slave attributes 3
PERI_MS_PPU_FX263_MS_ADDR	0x400249E0	READ	Master region, base address
PERI_MS_PPU_FX263_MS_SIZE	0x400249E4	READ	Master region, size
PERI_MS_PPU_FX263_MS_ATT0	0x400249F0	READ	Master attributes 0
PERI_MS_PPU_FX263_MS_ATT1	0x400249F4	READ	Master attributes 1
PERI_MS_PPU_FX263_MS_ATT2	0x400249F8	READ	Master attributes 2
PERI_MS_PPU_FX263_MS_ATT3	0x400249FC	READ	Master attributes 3

21.281 PPU_FX 264

Register Name	Address	Permission	Description
PERI_MS_PPU_FX264_SL_ADDR	0x40024A00	FULL	Slave region, base address
PERI_MS_PPU_FX264_SL_SIZE	0x40024A04	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX264_SL_ATT0	0x40024A10	FULL	Slave attributes 0
PERI_MS_PPU_FX264_SL_ATT1	0x40024A14	FULL	Slave attributes 1
PERI_MS_PPU_FX264_SL_ATT2	0x40024A18	FULL	Slave attributes 2
PERI_MS_PPU_FX264_SL_ATT3	0x40024A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX264_MS_ADDR	0x40024A20	FULL	Master region, base address
PERI_MS_PPU_FX264_MS_SIZE	0x40024A24	FULL	Master region, size
PERI_MS_PPU_FX264_MS_ATT0	0x40024A30	FULL	Master attributes 0
PERI_MS_PPU_FX264_MS_ATT1	0x40024A34	FULL	Master attributes 1
PERI_MS_PPU_FX264_MS_ATT2	0x40024A38	FULL	Master attributes 2
PERI_MS_PPU_FX264_MS_ATT3	0x40024A3C	FULL	Master attributes 3

21.282 PPU_FX 265

Register Name	Address	Permission	Description
PERI_MS_PPU_FX265_SL_ADDR	0x40024A40	FULL	Slave region, base address
PERI_MS_PPU_FX265_SL_SIZE	0x40024A44	FULL	Slave region, size
PERI_MS_PPU_FX265_SL_ATT0	0x40024A50	FULL	Slave attributes 0
PERI_MS_PPU_FX265_SL_ATT1	0x40024A54	FULL	Slave attributes 1
PERI_MS_PPU_FX265_SL_ATT2	0x40024A58	FULL	Slave attributes 2
PERI_MS_PPU_FX265_SL_ATT3	0x40024A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX265_MS_ADDR	0x40024A60	FULL	Master region, base address
PERI_MS_PPU_FX265_MS_SIZE	0x40024A64	FULL	Master region, size
PERI_MS_PPU_FX265_MS_ATT0	0x40024A70	FULL	Master attributes 0
PERI_MS_PPU_FX265_MS_ATT1	0x40024A74	FULL	Master attributes 1
PERI_MS_PPU_FX265_MS_ATT2	0x40024A78	FULL	Master attributes 2
PERI_MS_PPU_FX265_MS_ATT3	0x40024A7C	FULL	Master attributes 3

21.283 PPU_FX 266

Register Name	Address	Permission	Description
PERI_MS_PPU_FX266_SL_ADDR	0x40024A80	FULL	Slave region, base address
PERI_MS_PPU_FX266_SL_SIZE	0x40024A84	FULL	Slave region, size
PERI_MS_PPU_FX266_SL_ATT0	0x40024A90	FULL	Slave attributes 0
PERI_MS_PPU_FX266_SL_ATT1	0x40024A94	FULL	Slave attributes 1
PERI_MS_PPU_FX266_SL_ATT2	0x40024A98	FULL	Slave attributes 2
PERI_MS_PPU_FX266_SL_ATT3	0x40024A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX266_MS_ADDR	0x40024AA0	FULL	Master region, base address
PERI_MS_PPU_FX266_MS_SIZE	0x40024AA4	FULL	Master region, size
PERI_MS_PPU_FX266_MS_ATT0	0x40024AB0	FULL	Master attributes 0
PERI_MS_PPU_FX266_MS_ATT1	0x40024AB4	FULL	Master attributes 1
PERI_MS_PPU_FX266_MS_ATT2	0x40024AB8	FULL	Master attributes 2
PERI_MS_PPU_FX266_MS_ATT3	0x40024ABC	FULL	Master attributes 3

21.284 PPU_FX 267

Register Name	Address	Permission	Description
PERI_MS_PPU_FX267_SL_ADDR	0x40024AC0	FULL	Slave region, base address
PERI_MS_PPU_FX267_SL_SIZE	0x40024AC4	FULL	Slave region, size
PERI_MS_PPU_FX267_SL_ATT0	0x40024AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX267_SL_ATT1	0x40024AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX267_SL_ATT2	0x40024AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX267_SL_ATT3	0x40024ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX267_MS_ADDR	0x40024AE0	FULL	Master region, base address
PERI_MS_PPU_FX267_MS_SIZE	0x40024AE4	FULL	Master region, size
PERI_MS_PPU_FX267_MS_ATT0	0x40024AF0	FULL	Master attributes 0
PERI_MS_PPU_FX267_MS_ATT1	0x40024AF4	FULL	Master attributes 1
PERI_MS_PPU_FX267_MS_ATT2	0x40024AF8	FULL	Master attributes 2
PERI_MS_PPU_FX267_MS_ATT3	0x40024AFC	FULL	Master attributes 3

21.285 PPU_FX 268

Register Name	Address	Permission	Description
PERI_MS_PPU_FX268_SL_ADDR	0x40024B00	FULL	Slave region, base address
PERI_MS_PPU_FX268_SL_SIZE	0x40024B04	FULL	Slave region, size
PERI_MS_PPU_FX268_SL_ATT0	0x40024B10	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX268_SL_ATT1	0x40024B14	FULL	Slave attributes 1
PERI_MS_PPU_FX268_SL_ATT2	0x40024B18	FULL	Slave attributes 2
PERI_MS_PPU_FX268_SL_ATT3	0x40024B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX268_MS_ADDR	0x40024B20	FULL	Master region, base address
PERI_MS_PPU_FX268_MS_SIZE	0x40024B24	FULL	Master region, size
PERI_MS_PPU_FX268_MS_ATT0	0x40024B30	FULL	Master attributes 0
PERI_MS_PPU_FX268_MS_ATT1	0x40024B34	FULL	Master attributes 1
PERI_MS_PPU_FX268_MS_ATT2	0x40024B38	FULL	Master attributes 2
PERI_MS_PPU_FX268_MS_ATT3	0x40024B3C	FULL	Master attributes 3

21.286 PPU_FX 269

Register Name	Address	Permission	Description
PERI_MS_PPU_FX269_SL_ADDR	0x40024B40	FULL	Slave region, base address
PERI_MS_PPU_FX269_SL_SIZE	0x40024B44	FULL	Slave region, size
PERI_MS_PPU_FX269_SL_ATT0	0x40024B50	FULL	Slave attributes 0
PERI_MS_PPU_FX269_SL_ATT1	0x40024B54	FULL	Slave attributes 1
PERI_MS_PPU_FX269_SL_ATT2	0x40024B58	FULL	Slave attributes 2
PERI_MS_PPU_FX269_SL_ATT3	0x40024B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX269_MS_ADDR	0x40024B60	FULL	Master region, base address
PERI_MS_PPU_FX269_MS_SIZE	0x40024B64	FULL	Master region, size
PERI_MS_PPU_FX269_MS_ATT0	0x40024B70	FULL	Master attributes 0
PERI_MS_PPU_FX269_MS_ATT1	0x40024B74	FULL	Master attributes 1
PERI_MS_PPU_FX269_MS_ATT2	0x40024B78	FULL	Master attributes 2
PERI_MS_PPU_FX269_MS_ATT3	0x40024B7C	FULL	Master attributes 3

21.287 PPU_FX 270

Register Name	Address	Permission	Description
PERI_MS_PPU_FX270_SL_ADDR	0x40024B80	FULL	Slave region, base address
PERI_MS_PPU_FX270_SL_SIZE	0x40024B84	FULL	Slave region, size
PERI_MS_PPU_FX270_SL_ATT0	0x40024B90	FULL	Slave attributes 0
PERI_MS_PPU_FX270_SL_ATT1	0x40024B94	FULL	Slave attributes 1
PERI_MS_PPU_FX270_SL_ATT2	0x40024B98	FULL	Slave attributes 2
PERI_MS_PPU_FX270_SL_ATT3	0x40024B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX270_MS_ADDR	0x40024BA0	FULL	Master region, base address
PERI_MS_PPU_FX270_MS_SIZE	0x40024BA4	FULL	Master region, size
PERI_MS_PPU_FX270_MS_ATT0	0x40024BB0	FULL	Master attributes 0
PERI_MS_PPU_FX270_MS_ATT1	0x40024BB4	FULL	Master attributes 1
PERI_MS_PPU_FX270_MS_ATT2	0x40024BB8	FULL	Master attributes 2
PERI_MS_PPU_FX270_MS_ATT3	0x40024BBC	FULL	Master attributes 3

21.288 PPU_FX 271

Register Name	Address	Permission	Description
PERI_MS_PPU_FX271_SL_ADDR	0x40024BC0	FULL	Slave region, base address
PERI_MS_PPU_FX271_SL_SIZE	0x40024BC4	FULL	Slave region, size
PERI_MS_PPU_FX271_SL_ATT0	0x40024BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX271_SL_ATT1	0x40024BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX271_SL_ATT2	0x40024BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX271_SL_ATT3	0x40024BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX271_MS_ADDR	0x40024BE0	FULL	Master region, base address
PERI_MS_PPU_FX271_MS_SIZE	0x40024BE4	FULL	Master region, size
PERI_MS_PPU_FX271_MS_ATT0	0x40024BF0	FULL	Master attributes 0
PERI_MS_PPU_FX271_MS_ATT1	0x40024BF4	FULL	Master attributes 1
PERI_MS_PPU_FX271_MS_ATT2	0x40024BF8	FULL	Master attributes 2
PERI_MS_PPU_FX271_MS_ATT3	0x40024BFC	FULL	Master attributes 3

21.289 PPU_FX 272

Register Name	Address	Permission	Description
PERI_MS_PPU_FX272_SL_ADDR	0x40024C00	FULL	Slave region, base address
PERI_MS_PPU_FX272_SL_SIZE	0x40024C04	FULL	Slave region, size
PERI_MS_PPU_FX272_SL_ATT0	0x40024C10	FULL	Slave attributes 0
PERI_MS_PPU_FX272_SL_ATT1	0x40024C14	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX272_SL_ATT2	0x40024C18	FULL	Slave attributes 2
PERI_MS_PPU_FX272_SL_ATT3	0x40024C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX272_MS_ADDR	0x40024C20	FULL	Master region, base address
PERI_MS_PPU_FX272_MS_SIZE	0x40024C24	FULL	Master region, size
PERI_MS_PPU_FX272_MS_ATT0	0x40024C30	FULL	Master attributes 0
PERI_MS_PPU_FX272_MS_ATT1	0x40024C34	FULL	Master attributes 1
PERI_MS_PPU_FX272_MS_ATT2	0x40024C38	FULL	Master attributes 2
PERI_MS_PPU_FX272_MS_ATT3	0x40024C3C	FULL	Master attributes 3

21.290 PPU_FX 273

Register Name	Address	Permission	Description
PERI_MS_PPU_FX273_SL_ADDR	0x40024C40	FULL	Slave region, base address
PERI_MS_PPU_FX273_SL_SIZE	0x40024C44	FULL	Slave region, size
PERI_MS_PPU_FX273_SL_ATT0	0x40024C50	FULL	Slave attributes 0
PERI_MS_PPU_FX273_SL_ATT1	0x40024C54	FULL	Slave attributes 1
PERI_MS_PPU_FX273_SL_ATT2	0x40024C58	FULL	Slave attributes 2
PERI_MS_PPU_FX273_SL_ATT3	0x40024C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX273_MS_ADDR	0x40024C60	FULL	Master region, base address
PERI_MS_PPU_FX273_MS_SIZE	0x40024C64	FULL	Master region, size
PERI_MS_PPU_FX273_MS_ATT0	0x40024C70	FULL	Master attributes 0
PERI_MS_PPU_FX273_MS_ATT1	0x40024C74	FULL	Master attributes 1
PERI_MS_PPU_FX273_MS_ATT2	0x40024C78	FULL	Master attributes 2
PERI_MS_PPU_FX273_MS_ATT3	0x40024C7C	FULL	Master attributes 3

21.291 PPU_FX 274

Register Name	Address	Permission	Description
PERI_MS_PPU_FX274_SL_ADDR	0x40024C80	FULL	Slave region, base address
PERI_MS_PPU_FX274_SL_SIZE	0x40024C84	FULL	Slave region, size
PERI_MS_PPU_FX274_SL_ATT0	0x40024C90	FULL	Slave attributes 0
PERI_MS_PPU_FX274_SL_ATT1	0x40024C94	FULL	Slave attributes 1
PERI_MS_PPU_FX274_SL_ATT2	0x40024C98	FULL	Slave attributes 2
PERI_MS_PPU_FX274_SL_ATT3	0x40024C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX274_MS_ADDR	0x40024CA0	FULL	Master region, base address
PERI_MS_PPU_FX274_MS_SIZE	0x40024CA4	FULL	Master region, size
PERI_MS_PPU_FX274_MS_ATT0	0x40024CB0	FULL	Master attributes 0
PERI_MS_PPU_FX274_MS_ATT1	0x40024CB4	FULL	Master attributes 1
PERI_MS_PPU_FX274_MS_ATT2	0x40024CB8	FULL	Master attributes 2
PERI_MS_PPU_FX274_MS_ATT3	0x40024CBC	FULL	Master attributes 3

21.292 PPU_FX 275

Register Name	Address	Permission	Description
PERI_MS_PPU_FX275_SL_ADDR	0x40024CC0	FULL	Slave region, base address
PERI_MS_PPU_FX275_SL_SIZE	0x40024CC4	FULL	Slave region, size
PERI_MS_PPU_FX275_SL_ATT0	0x40024CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX275_SL_ATT1	0x40024CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX275_SL_ATT2	0x40024CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX275_SL_ATT3	0x40024CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX275_MS_ADDR	0x40024CE0	FULL	Master region, base address
PERI_MS_PPU_FX275_MS_SIZE	0x40024CE4	FULL	Master region, size
PERI_MS_PPU_FX275_MS_ATT0	0x40024CF0	FULL	Master attributes 0
PERI_MS_PPU_FX275_MS_ATT1	0x40024CF4	FULL	Master attributes 1
PERI_MS_PPU_FX275_MS_ATT2	0x40024CF8	FULL	Master attributes 2
PERI_MS_PPU_FX275_MS_ATT3	0x40024CFC	FULL	Master attributes 3

21.293 PPU_FX 276

Register Name	Address	Permission	Description
PERI_MS_PPU_FX276_SL_ADDR	0x40024D00	FULL	Slave region, base address
PERI_MS_PPU_FX276_SL_SIZE	0x40024D04	FULL	Slave region, size
PERI_MS_PPU_FX276_SL_ATT0	0x40024D10	FULL	Slave attributes 0
PERI_MS_PPU_FX276_SL_ATT1	0x40024D14	FULL	Slave attributes 1
PERI_MS_PPU_FX276_SL_ATT2	0x40024D18	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX276_SL_ATT3	0x40024D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX276_MS_ADDR	0x40024D20	FULL	Master region, base address
PERI_MS_PPU_FX276_MS_SIZE	0x40024D24	FULL	Master region, size
PERI_MS_PPU_FX276_MS_ATT0	0x40024D30	FULL	Master attributes 0
PERI_MS_PPU_FX276_MS_ATT1	0x40024D34	FULL	Master attributes 1
PERI_MS_PPU_FX276_MS_ATT2	0x40024D38	FULL	Master attributes 2
PERI_MS_PPU_FX276_MS_ATT3	0x40024D3C	FULL	Master attributes 3

21.294 PPU_FX 277

Register Name	Address	Permission	Description
PERI_MS_PPU_FX277_SL_ADDR	0x40024D40	FULL	Slave region, base address
PERI_MS_PPU_FX277_SL_SIZE	0x40024D44	FULL	Slave region, size
PERI_MS_PPU_FX277_SL_ATT0	0x40024D50	FULL	Slave attributes 0
PERI_MS_PPU_FX277_SL_ATT1	0x40024D54	FULL	Slave attributes 1
PERI_MS_PPU_FX277_SL_ATT2	0x40024D58	FULL	Slave attributes 2
PERI_MS_PPU_FX277_SL_ATT3	0x40024D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX277_MS_ADDR	0x40024D60	FULL	Master region, base address
PERI_MS_PPU_FX277_MS_SIZE	0x40024D64	FULL	Master region, size
PERI_MS_PPU_FX277_MS_ATT0	0x40024D70	FULL	Master attributes 0
PERI_MS_PPU_FX277_MS_ATT1	0x40024D74	FULL	Master attributes 1
PERI_MS_PPU_FX277_MS_ATT2	0x40024D78	FULL	Master attributes 2
PERI_MS_PPU_FX277_MS_ATT3	0x40024D7C	FULL	Master attributes 3

21.295 PPU_FX 278

Register Name	Address	Permission	Description
PERI_MS_PPU_FX278_SL_ADDR	0x40024D80	FULL	Slave region, base address
PERI_MS_PPU_FX278_SL_SIZE	0x40024D84	FULL	Slave region, size
PERI_MS_PPU_FX278_SL_ATT0	0x40024D90	FULL	Slave attributes 0
PERI_MS_PPU_FX278_SL_ATT1	0x40024D94	FULL	Slave attributes 1
PERI_MS_PPU_FX278_SL_ATT2	0x40024D98	FULL	Slave attributes 2
PERI_MS_PPU_FX278_SL_ATT3	0x40024D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX278_MS_ADDR	0x40024DA0	FULL	Master region, base address
PERI_MS_PPU_FX278_MS_SIZE	0x40024DA4	FULL	Master region, size
PERI_MS_PPU_FX278_MS_ATT0	0x40024DB0	FULL	Master attributes 0
PERI_MS_PPU_FX278_MS_ATT1	0x40024DB4	FULL	Master attributes 1
PERI_MS_PPU_FX278_MS_ATT2	0x40024DB8	FULL	Master attributes 2
PERI_MS_PPU_FX278_MS_ATT3	0x40024DBC	FULL	Master attributes 3

21.296 PPU_FX 279

Register Name	Address	Permission	Description
PERI_MS_PPU_FX279_SL_ADDR	0x40024DC0	FULL	Slave region, base address
PERI_MS_PPU_FX279_SL_SIZE	0x40024DC4	FULL	Slave region, size
PERI_MS_PPU_FX279_SL_ATT0	0x40024DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX279_SL_ATT1	0x40024DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX279_SL_ATT2	0x40024DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX279_SL_ATT3	0x40024DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX279_MS_ADDR	0x40024DE0	FULL	Master region, base address
PERI_MS_PPU_FX279_MS_SIZE	0x40024DE4	FULL	Master region, size
PERI_MS_PPU_FX279_MS_ATT0	0x40024DF0	FULL	Master attributes 0
PERI_MS_PPU_FX279_MS_ATT1	0x40024DF4	FULL	Master attributes 1
PERI_MS_PPU_FX279_MS_ATT2	0x40024DF8	FULL	Master attributes 2
PERI_MS_PPU_FX279_MS_ATT3	0x40024DFC	FULL	Master attributes 3

21.297 PPU_FX 280

Register Name	Address	Permission	Description
PERI_MS_PPU_FX280_SL_ADDR	0x40024E00	FULL	Slave region, base address
PERI_MS_PPU_FX280_SL_SIZE	0x40024E04	FULL	Slave region, size
PERI_MS_PPU_FX280_SL_ATT0	0x40024E10	FULL	Slave attributes 0
PERI_MS_PPU_FX280_SL_ATT1	0x40024E14	FULL	Slave attributes 1
PERI_MS_PPU_FX280_SL_ATT2	0x40024E18	FULL	Slave attributes 2
PERI_MS_PPU_FX280_SL_ATT3	0x40024E1C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX280_MS_ADDR	0x40024E20	FULL	Master region, base address
PERI_MS_PPU_FX280_MS_SIZE	0x40024E24	FULL	Master region, size
PERI_MS_PPU_FX280_MS_ATT0	0x40024E30	FULL	Master attributes 0
PERI_MS_PPU_FX280_MS_ATT1	0x40024E34	FULL	Master attributes 1
PERI_MS_PPU_FX280_MS_ATT2	0x40024E38	FULL	Master attributes 2
PERI_MS_PPU_FX280_MS_ATT3	0x40024E3C	FULL	Master attributes 3

21.298 PPU_FX 281

Register Name	Address	Permission	Description
PERI_MS_PPU_FX281_SL_ADDR	0x40024E40	FULL	Slave region, base address
PERI_MS_PPU_FX281_SL_SIZE	0x40024E44	FULL	Slave region, size
PERI_MS_PPU_FX281_SL_ATT0	0x40024E50	FULL	Slave attributes 0
PERI_MS_PPU_FX281_SL_ATT1	0x40024E54	FULL	Slave attributes 1
PERI_MS_PPU_FX281_SL_ATT2	0x40024E58	FULL	Slave attributes 2
PERI_MS_PPU_FX281_SL_ATT3	0x40024E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX281_MS_ADDR	0x40024E60	FULL	Master region, base address
PERI_MS_PPU_FX281_MS_SIZE	0x40024E64	FULL	Master region, size
PERI_MS_PPU_FX281_MS_ATT0	0x40024E70	FULL	Master attributes 0
PERI_MS_PPU_FX281_MS_ATT1	0x40024E74	FULL	Master attributes 1
PERI_MS_PPU_FX281_MS_ATT2	0x40024E78	FULL	Master attributes 2
PERI_MS_PPU_FX281_MS_ATT3	0x40024E7C	FULL	Master attributes 3

21.299 PPU_FX 282

Register Name	Address	Permission	Description
PERI_MS_PPU_FX282_SL_ADDR	0x40024E80	FULL	Slave region, base address
PERI_MS_PPU_FX282_SL_SIZE	0x40024E84	FULL	Slave region, size
PERI_MS_PPU_FX282_SL_ATT0	0x40024E90	FULL	Slave attributes 0
PERI_MS_PPU_FX282_SL_ATT1	0x40024E94	FULL	Slave attributes 1
PERI_MS_PPU_FX282_SL_ATT2	0x40024E98	FULL	Slave attributes 2
PERI_MS_PPU_FX282_SL_ATT3	0x40024E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX282_MS_ADDR	0x40024EA0	FULL	Master region, base address
PERI_MS_PPU_FX282_MS_SIZE	0x40024EA4	FULL	Master region, size
PERI_MS_PPU_FX282_MS_ATT0	0x40024EB0	FULL	Master attributes 0
PERI_MS_PPU_FX282_MS_ATT1	0x40024EB4	FULL	Master attributes 1
PERI_MS_PPU_FX282_MS_ATT2	0x40024EB8	FULL	Master attributes 2
PERI_MS_PPU_FX282_MS_ATT3	0x40024EBC	FULL	Master attributes 3

21.300 PPU_FX 283

Register Name	Address	Permission	Description
PERI_MS_PPU_FX283_SL_ADDR	0x40024EC0	FULL	Slave region, base address
PERI_MS_PPU_FX283_SL_SIZE	0x40024EC4	FULL	Slave region, size
PERI_MS_PPU_FX283_SL_ATT0	0x40024ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX283_SL_ATT1	0x40024ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX283_SL_ATT2	0x40024ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX283_SL_ATT3	0x40024EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX283_MS_ADDR	0x40024EE0	FULL	Master region, base address
PERI_MS_PPU_FX283_MS_SIZE	0x40024EE4	FULL	Master region, size
PERI_MS_PPU_FX283_MS_ATT0	0x40024EF0	FULL	Master attributes 0
PERI_MS_PPU_FX283_MS_ATT1	0x40024EF4	FULL	Master attributes 1
PERI_MS_PPU_FX283_MS_ATT2	0x40024EF8	FULL	Master attributes 2
PERI_MS_PPU_FX283_MS_ATT3	0x40024EFC	FULL	Master attributes 3

21.301 PPU_FX 284

Register Name	Address	Permission	Description
PERI_MS_PPU_FX284_SL_ADDR	0x40024F00	FULL	Slave region, base address
PERI_MS_PPU_FX284_SL_SIZE	0x40024F04	FULL	Slave region, size
PERI_MS_PPU_FX284_SL_ATT0	0x40024F10	FULL	Slave attributes 0
PERI_MS_PPU_FX284_SL_ATT1	0x40024F14	FULL	Slave attributes 1
PERI_MS_PPU_FX284_SL_ATT2	0x40024F18	FULL	Slave attributes 2
PERI_MS_PPU_FX284_SL_ATT3	0x40024F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX284_MS_ADDR	0x40024F20	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX284_MS_SIZE	0x40024F24	FULL	Master region, size
PERI_MS_PPU_FX284_MS_ATT0	0x40024F30	FULL	Master attributes 0
PERI_MS_PPU_FX284_MS_ATT1	0x40024F34	FULL	Master attributes 1
PERI_MS_PPU_FX284_MS_ATT2	0x40024F38	FULL	Master attributes 2
PERI_MS_PPU_FX284_MS_ATT3	0x40024F3C	FULL	Master attributes 3

21.302 PPU_FX 285

Register Name	Address	Permission	Description
PERI_MS_PPU_FX285_SL_ADDR	0x40024F40	FULL	Slave region, base address
PERI_MS_PPU_FX285_SL_SIZE	0x40024F44	FULL	Slave region, size
PERI_MS_PPU_FX285_SL_ATT0	0x40024F50	FULL	Slave attributes 0
PERI_MS_PPU_FX285_SL_ATT1	0x40024F54	FULL	Slave attributes 1
PERI_MS_PPU_FX285_SL_ATT2	0x40024F58	FULL	Slave attributes 2
PERI_MS_PPU_FX285_SL_ATT3	0x40024F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX285_MS_ADDR	0x40024F60	FULL	Master region, base address
PERI_MS_PPU_FX285_MS_SIZE	0x40024F64	FULL	Master region, size
PERI_MS_PPU_FX285_MS_ATT0	0x40024F70	FULL	Master attributes 0
PERI_MS_PPU_FX285_MS_ATT1	0x40024F74	FULL	Master attributes 1
PERI_MS_PPU_FX285_MS_ATT2	0x40024F78	FULL	Master attributes 2
PERI_MS_PPU_FX285_MS_ATT3	0x40024F7C	FULL	Master attributes 3

21.303 PPU_FX 286

Register Name	Address	Permission	Description
PERI_MS_PPU_FX286_SL_ADDR	0x40024F80	FULL	Slave region, base address
PERI_MS_PPU_FX286_SL_SIZE	0x40024F84	FULL	Slave region, size
PERI_MS_PPU_FX286_SL_ATT0	0x40024F90	FULL	Slave attributes 0
PERI_MS_PPU_FX286_SL_ATT1	0x40024F94	FULL	Slave attributes 1
PERI_MS_PPU_FX286_SL_ATT2	0x40024F98	FULL	Slave attributes 2
PERI_MS_PPU_FX286_SL_ATT3	0x40024F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX286_MS_ADDR	0x40024FA0	FULL	Master region, base address
PERI_MS_PPU_FX286_MS_SIZE	0x40024FA4	FULL	Master region, size
PERI_MS_PPU_FX286_MS_ATT0	0x40024FB0	FULL	Master attributes 0
PERI_MS_PPU_FX286_MS_ATT1	0x40024FB4	FULL	Master attributes 1
PERI_MS_PPU_FX286_MS_ATT2	0x40024FB8	FULL	Master attributes 2
PERI_MS_PPU_FX286_MS_ATT3	0x40024FBC	FULL	Master attributes 3

21.304 PPU_FX 287

Register Name	Address	Permission	Description
PERI_MS_PPU_FX287_SL_ADDR	0x40024FC0	FULL	Slave region, base address
PERI_MS_PPU_FX287_SL_SIZE	0x40024FC4	FULL	Slave region, size
PERI_MS_PPU_FX287_SL_ATT0	0x40024FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX287_SL_ATT1	0x40024FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX287_SL_ATT2	0x40024FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX287_SL_ATT3	0x40024FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX287_MS_ADDR	0x40024FE0	FULL	Master region, base address
PERI_MS_PPU_FX287_MS_SIZE	0x40024FE4	FULL	Master region, size
PERI_MS_PPU_FX287_MS_ATT0	0x40024FF0	FULL	Master attributes 0
PERI_MS_PPU_FX287_MS_ATT1	0x40024FF4	FULL	Master attributes 1
PERI_MS_PPU_FX287_MS_ATT2	0x40024FF8	FULL	Master attributes 2
PERI_MS_PPU_FX287_MS_ATT3	0x40024FFC	FULL	Master attributes 3

21.305 PPU_FX 288

Register Name	Address	Permission	Description
PERI_MS_PPU_FX288_SL_ADDR	0x40025000	FULL	Slave region, base address
PERI_MS_PPU_FX288_SL_SIZE	0x40025004	FULL	Slave region, size
PERI_MS_PPU_FX288_SL_ATT0	0x40025010	FULL	Slave attributes 0
PERI_MS_PPU_FX288_SL_ATT1	0x40025014	FULL	Slave attributes 1
PERI_MS_PPU_FX288_SL_ATT2	0x40025018	FULL	Slave attributes 2
PERI_MS_PPU_FX288_SL_ATT3	0x4002501C	FULL	Slave attributes 3
PERI_MS_PPU_FX288_MS_ADDR	0x40025020	FULL	Master region, base address
PERI_MS_PPU_FX288_MS_SIZE	0x40025024	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX288_MS_ATT0	0x40025030	FULL	Master attributes 0
PERI_MS_PPU_FX288_MS_ATT1	0x40025034	FULL	Master attributes 1
PERI_MS_PPU_FX288_MS_ATT2	0x40025038	FULL	Master attributes 2
PERI_MS_PPU_FX288_MS_ATT3	0x4002503C	FULL	Master attributes 3

21.306 PPU_FX 289

Register Name	Address	Permission	Description
PERI_MS_PPU_FX289_SL_ADDR	0x40025040	FULL	Slave region, base address
PERI_MS_PPU_FX289_SL_SIZE	0x40025044	FULL	Slave region, size
PERI_MS_PPU_FX289_SL_ATT0	0x40025050	FULL	Slave attributes 0
PERI_MS_PPU_FX289_SL_ATT1	0x40025054	FULL	Slave attributes 1
PERI_MS_PPU_FX289_SL_ATT2	0x40025058	FULL	Slave attributes 2
PERI_MS_PPU_FX289_SL_ATT3	0x4002505C	FULL	Slave attributes 3
PERI_MS_PPU_FX289_MS_ADDR	0x40025060	FULL	Master region, base address
PERI_MS_PPU_FX289_MS_SIZE	0x40025064	FULL	Master region, size
PERI_MS_PPU_FX289_MS_ATT0	0x40025070	FULL	Master attributes 0
PERI_MS_PPU_FX289_MS_ATT1	0x40025074	FULL	Master attributes 1
PERI_MS_PPU_FX289_MS_ATT2	0x40025078	FULL	Master attributes 2
PERI_MS_PPU_FX289_MS_ATT3	0x4002507C	FULL	Master attributes 3

21.307 PPU_FX 290

Register Name	Address	Permission	Description
PERI_MS_PPU_FX290_SL_ADDR	0x40025080	FULL	Slave region, base address
PERI_MS_PPU_FX290_SL_SIZE	0x40025084	FULL	Slave region, size
PERI_MS_PPU_FX290_SL_ATT0	0x40025090	FULL	Slave attributes 0
PERI_MS_PPU_FX290_SL_ATT1	0x40025094	FULL	Slave attributes 1
PERI_MS_PPU_FX290_SL_ATT2	0x40025098	FULL	Slave attributes 2
PERI_MS_PPU_FX290_SL_ATT3	0x4002509C	FULL	Slave attributes 3
PERI_MS_PPU_FX290_MS_ADDR	0x400250A0	FULL	Master region, base address
PERI_MS_PPU_FX290_MS_SIZE	0x400250A4	FULL	Master region, size
PERI_MS_PPU_FX290_MS_ATT0	0x400250B0	FULL	Master attributes 0
PERI_MS_PPU_FX290_MS_ATT1	0x400250B4	FULL	Master attributes 1
PERI_MS_PPU_FX290_MS_ATT2	0x400250B8	FULL	Master attributes 2
PERI_MS_PPU_FX290_MS_ATT3	0x400250BC	FULL	Master attributes 3

21.308 PPU_FX 291

Register Name	Address	Permission	Description
PERI_MS_PPU_FX291_SL_ADDR	0x400250C0	FULL	Slave region, base address
PERI_MS_PPU_FX291_SL_SIZE	0x400250C4	FULL	Slave region, size
PERI_MS_PPU_FX291_SL_ATT0	0x400250D0	FULL	Slave attributes 0
PERI_MS_PPU_FX291_SL_ATT1	0x400250D4	FULL	Slave attributes 1
PERI_MS_PPU_FX291_SL_ATT2	0x400250D8	FULL	Slave attributes 2
PERI_MS_PPU_FX291_SL_ATT3	0x400250DC	FULL	Slave attributes 3
PERI_MS_PPU_FX291_MS_ADDR	0x400250E0	FULL	Master region, base address
PERI_MS_PPU_FX291_MS_SIZE	0x400250E4	FULL	Master region, size
PERI_MS_PPU_FX291_MS_ATT0	0x400250F0	FULL	Master attributes 0
PERI_MS_PPU_FX291_MS_ATT1	0x400250F4	FULL	Master attributes 1
PERI_MS_PPU_FX291_MS_ATT2	0x400250F8	FULL	Master attributes 2
PERI_MS_PPU_FX291_MS_ATT3	0x400250FC	FULL	Master attributes 3

21.309 PPU_FX 292

Register Name	Address	Permission	Description
PERI_MS_PPU_FX292_SL_ADDR	0x40025100	FULL	Slave region, base address
PERI_MS_PPU_FX292_SL_SIZE	0x40025104	FULL	Slave region, size
PERI_MS_PPU_FX292_SL_ATT0	0x40025110	FULL	Slave attributes 0
PERI_MS_PPU_FX292_SL_ATT1	0x40025114	FULL	Slave attributes 1
PERI_MS_PPU_FX292_SL_ATT2	0x40025118	FULL	Slave attributes 2
PERI_MS_PPU_FX292_SL_ATT3	0x4002511C	FULL	Slave attributes 3
PERI_MS_PPU_FX292_MS_ADDR	0x40025120	FULL	Master region, base address
PERI_MS_PPU_FX292_MS_SIZE	0x40025124	FULL	Master region, size
PERI_MS_PPU_FX292_MS_ATT0	0x40025130	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX292_MS_ATT1	0x40025134	FULL	Master attributes 1
PERI_MS_PPU_FX292_MS_ATT2	0x40025138	FULL	Master attributes 2
PERI_MS_PPU_FX292_MS_ATT3	0x4002513C	FULL	Master attributes 3

21.310 PPU_FX 293

Register Name	Address	Permission	Description
PERI_MS_PPU_FX293_SL_ADDR	0x40025140	FULL	Slave region, base address
PERI_MS_PPU_FX293_SL_SIZE	0x40025144	FULL	Slave region, size
PERI_MS_PPU_FX293_SL_ATT0	0x40025150	FULL	Slave attributes 0
PERI_MS_PPU_FX293_SL_ATT1	0x40025154	FULL	Slave attributes 1
PERI_MS_PPU_FX293_SL_ATT2	0x40025158	FULL	Slave attributes 2
PERI_MS_PPU_FX293_SL_ATT3	0x4002515C	FULL	Slave attributes 3
PERI_MS_PPU_FX293_MS_ADDR	0x40025160	FULL	Master region, base address
PERI_MS_PPU_FX293_MS_SIZE	0x40025164	FULL	Master region, size
PERI_MS_PPU_FX293_MS_ATT0	0x40025170	FULL	Master attributes 0
PERI_MS_PPU_FX293_MS_ATT1	0x40025174	FULL	Master attributes 1
PERI_MS_PPU_FX293_MS_ATT2	0x40025178	FULL	Master attributes 2
PERI_MS_PPU_FX293_MS_ATT3	0x4002517C	FULL	Master attributes 3

21.311 PPU_FX 294

Register Name	Address	Permission	Description
PERI_MS_PPU_FX294_SL_ADDR	0x40025180	FULL	Slave region, base address
PERI_MS_PPU_FX294_SL_SIZE	0x40025184	FULL	Slave region, size
PERI_MS_PPU_FX294_SL_ATT0	0x40025190	FULL	Slave attributes 0
PERI_MS_PPU_FX294_SL_ATT1	0x40025194	FULL	Slave attributes 1
PERI_MS_PPU_FX294_SL_ATT2	0x40025198	FULL	Slave attributes 2
PERI_MS_PPU_FX294_SL_ATT3	0x4002519C	FULL	Slave attributes 3
PERI_MS_PPU_FX294_MS_ADDR	0x400251A0	FULL	Master region, base address
PERI_MS_PPU_FX294_MS_SIZE	0x400251A4	FULL	Master region, size
PERI_MS_PPU_FX294_MS_ATT0	0x400251B0	FULL	Master attributes 0
PERI_MS_PPU_FX294_MS_ATT1	0x400251B4	FULL	Master attributes 1
PERI_MS_PPU_FX294_MS_ATT2	0x400251B8	FULL	Master attributes 2
PERI_MS_PPU_FX294_MS_ATT3	0x400251BC	FULL	Master attributes 3

21.312 PPU_FX 295

Register Name	Address	Permission	Description
PERI_MS_PPU_FX295_SL_ADDR	0x400251C0	FULL	Slave region, base address
PERI_MS_PPU_FX295_SL_SIZE	0x400251C4	FULL	Slave region, size
PERI_MS_PPU_FX295_SL_ATT0	0x400251D0	FULL	Slave attributes 0
PERI_MS_PPU_FX295_SL_ATT1	0x400251D4	FULL	Slave attributes 1
PERI_MS_PPU_FX295_SL_ATT2	0x400251D8	FULL	Slave attributes 2
PERI_MS_PPU_FX295_SL_ATT3	0x400251DC	FULL	Slave attributes 3
PERI_MS_PPU_FX295_MS_ADDR	0x400251E0	FULL	Master region, base address
PERI_MS_PPU_FX295_MS_SIZE	0x400251E4	FULL	Master region, size
PERI_MS_PPU_FX295_MS_ATT0	0x400251F0	FULL	Master attributes 0
PERI_MS_PPU_FX295_MS_ATT1	0x400251F4	FULL	Master attributes 1
PERI_MS_PPU_FX295_MS_ATT2	0x400251F8	FULL	Master attributes 2
PERI_MS_PPU_FX295_MS_ATT3	0x400251FC	FULL	Master attributes 3

21.313 PPU_FX 296

Register Name	Address	Permission	Description
PERI_MS_PPU_FX296_SL_ADDR	0x40025200	FULL	Slave region, base address
PERI_MS_PPU_FX296_SL_SIZE	0x40025204	FULL	Slave region, size
PERI_MS_PPU_FX296_SL_ATT0	0x40025210	FULL	Slave attributes 0
PERI_MS_PPU_FX296_SL_ATT1	0x40025214	FULL	Slave attributes 1
PERI_MS_PPU_FX296_SL_ATT2	0x40025218	FULL	Slave attributes 2
PERI_MS_PPU_FX296_SL_ATT3	0x4002521C	FULL	Slave attributes 3
PERI_MS_PPU_FX296_MS_ADDR	0x40025220	FULL	Master region, base address
PERI_MS_PPU_FX296_MS_SIZE	0x40025224	FULL	Master region, size
PERI_MS_PPU_FX296_MS_ATT0	0x40025230	FULL	Master attributes 0
PERI_MS_PPU_FX296_MS_ATT1	0x40025234	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX296_MS_ATT2	0x40025238	FULL	Master attributes 2
PERI_MS_PPU_FX296_MS_ATT3	0x4002523C	FULL	Master attributes 3

21.314 PPU_FX 297

Register Name	Address	Permission	Description
PERI_MS_PPU_FX297_SL_ADDR	0x40025240	FULL	Slave region, base address
PERI_MS_PPU_FX297_SL_SIZE	0x40025244	FULL	Slave region, size
PERI_MS_PPU_FX297_SL_ATT0	0x40025250	FULL	Slave attributes 0
PERI_MS_PPU_FX297_SL_ATT1	0x40025254	FULL	Slave attributes 1
PERI_MS_PPU_FX297_SL_ATT2	0x40025258	FULL	Slave attributes 2
PERI_MS_PPU_FX297_SL_ATT3	0x4002525C	FULL	Slave attributes 3
PERI_MS_PPU_FX297_MS_ADDR	0x40025260	FULL	Master region, base address
PERI_MS_PPU_FX297_MS_SIZE	0x40025264	FULL	Master region, size
PERI_MS_PPU_FX297_MS_ATT0	0x40025270	FULL	Master attributes 0
PERI_MS_PPU_FX297_MS_ATT1	0x40025274	FULL	Master attributes 1
PERI_MS_PPU_FX297_MS_ATT2	0x40025278	FULL	Master attributes 2
PERI_MS_PPU_FX297_MS_ATT3	0x4002527C	FULL	Master attributes 3

21.315 PPU_FX 298

Register Name	Address	Permission	Description
PERI_MS_PPU_FX298_SL_ADDR	0x40025280	FULL	Slave region, base address
PERI_MS_PPU_FX298_SL_SIZE	0x40025284	FULL	Slave region, size
PERI_MS_PPU_FX298_SL_ATT0	0x40025290	FULL	Slave attributes 0
PERI_MS_PPU_FX298_SL_ATT1	0x40025294	FULL	Slave attributes 1
PERI_MS_PPU_FX298_SL_ATT2	0x40025298	FULL	Slave attributes 2
PERI_MS_PPU_FX298_SL_ATT3	0x4002529C	FULL	Slave attributes 3
PERI_MS_PPU_FX298_MS_ADDR	0x400252A0	FULL	Master region, base address
PERI_MS_PPU_FX298_MS_SIZE	0x400252A4	FULL	Master region, size
PERI_MS_PPU_FX298_MS_ATT0	0x400252B0	FULL	Master attributes 0
PERI_MS_PPU_FX298_MS_ATT1	0x400252B4	FULL	Master attributes 1
PERI_MS_PPU_FX298_MS_ATT2	0x400252B8	FULL	Master attributes 2
PERI_MS_PPU_FX298_MS_ATT3	0x400252BC	FULL	Master attributes 3

21.316 PPU_FX 299

Register Name	Address	Permission	Description
PERI_MS_PPU_FX299_SL_ADDR	0x400252C0	FULL	Slave region, base address
PERI_MS_PPU_FX299_SL_SIZE	0x400252C4	FULL	Slave region, size
PERI_MS_PPU_FX299_SL_ATT0	0x400252D0	FULL	Slave attributes 0
PERI_MS_PPU_FX299_SL_ATT1	0x400252D4	FULL	Slave attributes 1
PERI_MS_PPU_FX299_SL_ATT2	0x400252D8	FULL	Slave attributes 2
PERI_MS_PPU_FX299_SL_ATT3	0x400252DC	FULL	Slave attributes 3
PERI_MS_PPU_FX299_MS_ADDR	0x400252E0	FULL	Master region, base address
PERI_MS_PPU_FX299_MS_SIZE	0x400252E4	FULL	Master region, size
PERI_MS_PPU_FX299_MS_ATT0	0x400252F0	FULL	Master attributes 0
PERI_MS_PPU_FX299_MS_ATT1	0x400252F4	FULL	Master attributes 1
PERI_MS_PPU_FX299_MS_ATT2	0x400252F8	FULL	Master attributes 2
PERI_MS_PPU_FX299_MS_ATT3	0x400252FC	FULL	Master attributes 3

21.317 PPU_FX 300

Register Name	Address	Permission	Description
PERI_MS_PPU_FX300_SL_ADDR	0x40025300	FULL	Slave region, base address
PERI_MS_PPU_FX300_SL_SIZE	0x40025304	FULL	Slave region, size
PERI_MS_PPU_FX300_SL_ATT0	0x40025310	FULL	Slave attributes 0
PERI_MS_PPU_FX300_SL_ATT1	0x40025314	FULL	Slave attributes 1
PERI_MS_PPU_FX300_SL_ATT2	0x40025318	FULL	Slave attributes 2
PERI_MS_PPU_FX300_SL_ATT3	0x4002531C	FULL	Slave attributes 3
PERI_MS_PPU_FX300_MS_ADDR	0x40025320	FULL	Master region, base address
PERI_MS_PPU_FX300_MS_SIZE	0x40025324	FULL	Master region, size
PERI_MS_PPU_FX300_MS_ATT0	0x40025330	FULL	Master attributes 0
PERI_MS_PPU_FX300_MS_ATT1	0x40025334	FULL	Master attributes 1
PERI_MS_PPU_FX300_MS_ATT2	0x40025338	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX300_MS_ATT3	0x4002533C	FULL	Master attributes 3

21.318 PPU_FX 301

Register Name	Address	Permission	Description
PERI_MS_PPU_FX301_SL_ADDR	0x40025340	FULL	Slave region, base address
PERI_MS_PPU_FX301_SL_SIZE	0x40025344	FULL	Slave region, size
PERI_MS_PPU_FX301_SL_ATT0	0x40025350	FULL	Slave attributes 0
PERI_MS_PPU_FX301_SL_ATT1	0x40025354	FULL	Slave attributes 1
PERI_MS_PPU_FX301_SL_ATT2	0x40025358	FULL	Slave attributes 2
PERI_MS_PPU_FX301_SL_ATT3	0x4002535C	FULL	Slave attributes 3
PERI_MS_PPU_FX301_MS_ADDR	0x40025360	FULL	Master region, base address
PERI_MS_PPU_FX301_MS_SIZE	0x40025364	FULL	Master region, size
PERI_MS_PPU_FX301_MS_ATT0	0x40025370	FULL	Master attributes 0
PERI_MS_PPU_FX301_MS_ATT1	0x40025374	FULL	Master attributes 1
PERI_MS_PPU_FX301_MS_ATT2	0x40025378	FULL	Master attributes 2
PERI_MS_PPU_FX301_MS_ATT3	0x4002537C	FULL	Master attributes 3

21.319 PPU_FX 302

Register Name	Address	Permission	Description
PERI_MS_PPU_FX302_SL_ADDR	0x40025380	FULL	Slave region, base address
PERI_MS_PPU_FX302_SL_SIZE	0x40025384	FULL	Slave region, size
PERI_MS_PPU_FX302_SL_ATT0	0x40025390	FULL	Slave attributes 0
PERI_MS_PPU_FX302_SL_ATT1	0x40025394	FULL	Slave attributes 1
PERI_MS_PPU_FX302_SL_ATT2	0x40025398	FULL	Slave attributes 2
PERI_MS_PPU_FX302_SL_ATT3	0x4002539C	FULL	Slave attributes 3
PERI_MS_PPU_FX302_MS_ADDR	0x400253A0	FULL	Master region, base address
PERI_MS_PPU_FX302_MS_SIZE	0x400253A4	FULL	Master region, size
PERI_MS_PPU_FX302_MS_ATT0	0x400253B0	FULL	Master attributes 0
PERI_MS_PPU_FX302_MS_ATT1	0x400253B4	FULL	Master attributes 1
PERI_MS_PPU_FX302_MS_ATT2	0x400253B8	FULL	Master attributes 2
PERI_MS_PPU_FX302_MS_ATT3	0x400253BC	FULL	Master attributes 3

21.320 PPU_FX 303

Register Name	Address	Permission	Description
PERI_MS_PPU_FX303_SL_ADDR	0x400253C0	FULL	Slave region, base address
PERI_MS_PPU_FX303_SL_SIZE	0x400253C4	FULL	Slave region, size
PERI_MS_PPU_FX303_SL_ATT0	0x400253D0	FULL	Slave attributes 0
PERI_MS_PPU_FX303_SL_ATT1	0x400253D4	FULL	Slave attributes 1
PERI_MS_PPU_FX303_SL_ATT2	0x400253D8	FULL	Slave attributes 2
PERI_MS_PPU_FX303_SL_ATT3	0x400253DC	FULL	Slave attributes 3
PERI_MS_PPU_FX303_MS_ADDR	0x400253E0	FULL	Master region, base address
PERI_MS_PPU_FX303_MS_SIZE	0x400253E4	FULL	Master region, size
PERI_MS_PPU_FX303_MS_ATT0	0x400253F0	FULL	Master attributes 0
PERI_MS_PPU_FX303_MS_ATT1	0x400253F4	FULL	Master attributes 1
PERI_MS_PPU_FX303_MS_ATT2	0x400253F8	FULL	Master attributes 2
PERI_MS_PPU_FX303_MS_ATT3	0x400253FC	FULL	Master attributes 3

21.321 PPU_FX 304

Register Name	Address	Permission	Description
PERI_MS_PPU_FX304_SL_ADDR	0x40025400	FULL	Slave region, base address
PERI_MS_PPU_FX304_SL_SIZE	0x40025404	FULL	Slave region, size
PERI_MS_PPU_FX304_SL_ATT0	0x40025410	FULL	Slave attributes 0
PERI_MS_PPU_FX304_SL_ATT1	0x40025414	FULL	Slave attributes 1
PERI_MS_PPU_FX304_SL_ATT2	0x40025418	FULL	Slave attributes 2
PERI_MS_PPU_FX304_SL_ATT3	0x4002541C	FULL	Slave attributes 3
PERI_MS_PPU_FX304_MS_ADDR	0x40025420	FULL	Master region, base address
PERI_MS_PPU_FX304_MS_SIZE	0x40025424	FULL	Master region, size
PERI_MS_PPU_FX304_MS_ATT0	0x40025430	FULL	Master attributes 0
PERI_MS_PPU_FX304_MS_ATT1	0x40025434	FULL	Master attributes 1
PERI_MS_PPU_FX304_MS_ATT2	0x40025438	FULL	Master attributes 2
PERI_MS_PPU_FX304_MS_ATT3	0x4002543C	FULL	Master attributes 3

21.322 PPU_FX 305

Register Name	Address	Permission	Description
PERI_MS_PPU_FX305_SL_ADDR	0x40025440	FULL	Slave region, base address
PERI_MS_PPU_FX305_SL_SIZE	0x40025444	FULL	Slave region, size
PERI_MS_PPU_FX305_SL_ATT0	0x40025450	FULL	Slave attributes 0
PERI_MS_PPU_FX305_SL_ATT1	0x40025454	FULL	Slave attributes 1
PERI_MS_PPU_FX305_SL_ATT2	0x40025458	FULL	Slave attributes 2
PERI_MS_PPU_FX305_SL_ATT3	0x4002545C	FULL	Slave attributes 3
PERI_MS_PPU_FX305_MS_ADDR	0x40025460	FULL	Master region, base address
PERI_MS_PPU_FX305_MS_SIZE	0x40025464	FULL	Master region, size
PERI_MS_PPU_FX305_MS_ATT0	0x40025470	FULL	Master attributes 0
PERI_MS_PPU_FX305_MS_ATT1	0x40025474	FULL	Master attributes 1
PERI_MS_PPU_FX305_MS_ATT2	0x40025478	FULL	Master attributes 2
PERI_MS_PPU_FX305_MS_ATT3	0x4002547C	FULL	Master attributes 3

21.323 PPU_FX 306

Register Name	Address	Permission	Description
PERI_MS_PPU_FX306_SL_ADDR	0x40025480	FULL	Slave region, base address
PERI_MS_PPU_FX306_SL_SIZE	0x40025484	FULL	Slave region, size
PERI_MS_PPU_FX306_SL_ATT0	0x40025490	FULL	Slave attributes 0
PERI_MS_PPU_FX306_SL_ATT1	0x40025494	FULL	Slave attributes 1
PERI_MS_PPU_FX306_SL_ATT2	0x40025498	FULL	Slave attributes 2
PERI_MS_PPU_FX306_SL_ATT3	0x4002549C	FULL	Slave attributes 3
PERI_MS_PPU_FX306_MS_ADDR	0x400254A0	FULL	Master region, base address
PERI_MS_PPU_FX306_MS_SIZE	0x400254A4	FULL	Master region, size
PERI_MS_PPU_FX306_MS_ATT0	0x400254B0	FULL	Master attributes 0
PERI_MS_PPU_FX306_MS_ATT1	0x400254B4	FULL	Master attributes 1
PERI_MS_PPU_FX306_MS_ATT2	0x400254B8	FULL	Master attributes 2
PERI_MS_PPU_FX306_MS_ATT3	0x400254BC	FULL	Master attributes 3

21.324 PPU_FX 307

Register Name	Address	Permission	Description
PERI_MS_PPU_FX307_SL_ADDR	0x400254C0	FULL	Slave region, base address
PERI_MS_PPU_FX307_SL_SIZE	0x400254C4	FULL	Slave region, size
PERI_MS_PPU_FX307_SL_ATT0	0x400254D0	FULL	Slave attributes 0
PERI_MS_PPU_FX307_SL_ATT1	0x400254D4	FULL	Slave attributes 1
PERI_MS_PPU_FX307_SL_ATT2	0x400254D8	FULL	Slave attributes 2
PERI_MS_PPU_FX307_SL_ATT3	0x400254DC	FULL	Slave attributes 3
PERI_MS_PPU_FX307_MS_ADDR	0x400254E0	FULL	Master region, base address
PERI_MS_PPU_FX307_MS_SIZE	0x400254E4	FULL	Master region, size
PERI_MS_PPU_FX307_MS_ATT0	0x400254F0	FULL	Master attributes 0
PERI_MS_PPU_FX307_MS_ATT1	0x400254F4	FULL	Master attributes 1
PERI_MS_PPU_FX307_MS_ATT2	0x400254F8	FULL	Master attributes 2
PERI_MS_PPU_FX307_MS_ATT3	0x400254FC	FULL	Master attributes 3

21.325 PPU_FX 308

Register Name	Address	Permission	Description
PERI_MS_PPU_FX308_SL_ADDR	0x40025500	FULL	Slave region, base address
PERI_MS_PPU_FX308_SL_SIZE	0x40025504	FULL	Slave region, size
PERI_MS_PPU_FX308_SL_ATT0	0x40025510	FULL	Slave attributes 0
PERI_MS_PPU_FX308_SL_ATT1	0x40025514	FULL	Slave attributes 1
PERI_MS_PPU_FX308_SL_ATT2	0x40025518	FULL	Slave attributes 2
PERI_MS_PPU_FX308_SL_ATT3	0x4002551C	FULL	Slave attributes 3
PERI_MS_PPU_FX308_MS_ADDR	0x40025520	FULL	Master region, base address
PERI_MS_PPU_FX308_MS_SIZE	0x40025524	FULL	Master region, size
PERI_MS_PPU_FX308_MS_ATT0	0x40025530	FULL	Master attributes 0
PERI_MS_PPU_FX308_MS_ATT1	0x40025534	FULL	Master attributes 1
PERI_MS_PPU_FX308_MS_ATT2	0x40025538	FULL	Master attributes 2
PERI_MS_PPU_FX308_MS_ATT3	0x4002553C	FULL	Master attributes 3

21.326 PPU_FX 309

Register Name	Address	Permission	Description
PERI_MS_PPU_FX309_SL_ADDR	0x40025540	FULL	Slave region, base address
PERI_MS_PPU_FX309_SL_SIZE	0x40025544	FULL	Slave region, size
PERI_MS_PPU_FX309_SL_ATT0	0x40025550	FULL	Slave attributes 0
PERI_MS_PPU_FX309_SL_ATT1	0x40025554	FULL	Slave attributes 1
PERI_MS_PPU_FX309_SL_ATT2	0x40025558	FULL	Slave attributes 2
PERI_MS_PPU_FX309_SL_ATT3	0x4002555C	FULL	Slave attributes 3
PERI_MS_PPU_FX309_MS_ADDR	0x40025560	FULL	Master region, base address
PERI_MS_PPU_FX309_MS_SIZE	0x40025564	FULL	Master region, size
PERI_MS_PPU_FX309_MS_ATT0	0x40025570	FULL	Master attributes 0
PERI_MS_PPU_FX309_MS_ATT1	0x40025574	FULL	Master attributes 1
PERI_MS_PPU_FX309_MS_ATT2	0x40025578	FULL	Master attributes 2
PERI_MS_PPU_FX309_MS_ATT3	0x4002557C	FULL	Master attributes 3

21.327 PPU_FX 310

Register Name	Address	Permission	Description
PERI_MS_PPU_FX310_SL_ADDR	0x40025580	FULL	Slave region, base address
PERI_MS_PPU_FX310_SL_SIZE	0x40025584	FULL	Slave region, size
PERI_MS_PPU_FX310_SL_ATT0	0x40025590	FULL	Slave attributes 0
PERI_MS_PPU_FX310_SL_ATT1	0x40025594	FULL	Slave attributes 1
PERI_MS_PPU_FX310_SL_ATT2	0x40025598	FULL	Slave attributes 2
PERI_MS_PPU_FX310_SL_ATT3	0x4002559C	FULL	Slave attributes 3
PERI_MS_PPU_FX310_MS_ADDR	0x400255A0	FULL	Master region, base address
PERI_MS_PPU_FX310_MS_SIZE	0x400255A4	FULL	Master region, size
PERI_MS_PPU_FX310_MS_ATT0	0x400255B0	FULL	Master attributes 0
PERI_MS_PPU_FX310_MS_ATT1	0x400255B4	FULL	Master attributes 1
PERI_MS_PPU_FX310_MS_ATT2	0x400255B8	FULL	Master attributes 2
PERI_MS_PPU_FX310_MS_ATT3	0x400255BC	FULL	Master attributes 3

21.328 PPU_FX 311

Register Name	Address	Permission	Description
PERI_MS_PPU_FX311_SL_ADDR	0x400255C0	FULL	Slave region, base address
PERI_MS_PPU_FX311_SL_SIZE	0x400255C4	FULL	Slave region, size
PERI_MS_PPU_FX311_SL_ATT0	0x400255D0	FULL	Slave attributes 0
PERI_MS_PPU_FX311_SL_ATT1	0x400255D4	FULL	Slave attributes 1
PERI_MS_PPU_FX311_SL_ATT2	0x400255D8	FULL	Slave attributes 2
PERI_MS_PPU_FX311_SL_ATT3	0x400255DC	FULL	Slave attributes 3
PERI_MS_PPU_FX311_MS_ADDR	0x400255E0	FULL	Master region, base address
PERI_MS_PPU_FX311_MS_SIZE	0x400255E4	FULL	Master region, size
PERI_MS_PPU_FX311_MS_ATT0	0x400255F0	FULL	Master attributes 0
PERI_MS_PPU_FX311_MS_ATT1	0x400255F4	FULL	Master attributes 1
PERI_MS_PPU_FX311_MS_ATT2	0x400255F8	FULL	Master attributes 2
PERI_MS_PPU_FX311_MS_ATT3	0x400255FC	FULL	Master attributes 3

21.329 PPU_FX 312

Register Name	Address	Permission	Description
PERI_MS_PPU_FX312_SL_ADDR	0x40025600	FULL	Slave region, base address
PERI_MS_PPU_FX312_SL_SIZE	0x40025604	FULL	Slave region, size
PERI_MS_PPU_FX312_SL_ATT0	0x40025610	FULL	Slave attributes 0
PERI_MS_PPU_FX312_SL_ATT1	0x40025614	FULL	Slave attributes 1
PERI_MS_PPU_FX312_SL_ATT2	0x40025618	FULL	Slave attributes 2
PERI_MS_PPU_FX312_SL_ATT3	0x4002561C	FULL	Slave attributes 3
PERI_MS_PPU_FX312_MS_ADDR	0x40025620	FULL	Master region, base address
PERI_MS_PPU_FX312_MS_SIZE	0x40025624	FULL	Master region, size
PERI_MS_PPU_FX312_MS_ATT0	0x40025630	FULL	Master attributes 0
PERI_MS_PPU_FX312_MS_ATT1	0x40025634	FULL	Master attributes 1
PERI_MS_PPU_FX312_MS_ATT2	0x40025638	FULL	Master attributes 2
PERI_MS_PPU_FX312_MS_ATT3	0x4002563C	FULL	Master attributes 3

21.330 PPU_FX 313

Register Name	Address	Permission	Description
PERI_MS_PPU_FX313_SL_ADDR	0x40025640	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX313_SL_SIZE	0x40025644	FULL	Slave region, size
PERI_MS_PPU_FX313_SL_ATT0	0x40025650	FULL	Slave attributes 0
PERI_MS_PPU_FX313_SL_ATT1	0x40025654	FULL	Slave attributes 1
PERI_MS_PPU_FX313_SL_ATT2	0x40025658	FULL	Slave attributes 2
PERI_MS_PPU_FX313_SL_ATT3	0x4002565C	FULL	Slave attributes 3
PERI_MS_PPU_FX313_MS_ADDR	0x40025660	FULL	Master region, base address
PERI_MS_PPU_FX313_MS_SIZE	0x40025664	FULL	Master region, size
PERI_MS_PPU_FX313_MS_ATT0	0x40025670	FULL	Master attributes 0
PERI_MS_PPU_FX313_MS_ATT1	0x40025674	FULL	Master attributes 1
PERI_MS_PPU_FX313_MS_ATT2	0x40025678	FULL	Master attributes 2
PERI_MS_PPU_FX313_MS_ATT3	0x4002567C	FULL	Master attributes 3

21.331 PPU_FX 314

Register Name	Address	Permission	Description
PERI_MS_PPU_FX314_SL_ADDR	0x40025680	FULL	Slave region, base address
PERI_MS_PPU_FX314_SL_SIZE	0x40025684	FULL	Slave region, size
PERI_MS_PPU_FX314_SL_ATT0	0x40025690	FULL	Slave attributes 0
PERI_MS_PPU_FX314_SL_ATT1	0x40025694	FULL	Slave attributes 1
PERI_MS_PPU_FX314_SL_ATT2	0x40025698	FULL	Slave attributes 2
PERI_MS_PPU_FX314_SL_ATT3	0x4002569C	FULL	Slave attributes 3
PERI_MS_PPU_FX314_MS_ADDR	0x400256A0	FULL	Master region, base address
PERI_MS_PPU_FX314_MS_SIZE	0x400256A4	FULL	Master region, size
PERI_MS_PPU_FX314_MS_ATT0	0x400256B0	FULL	Master attributes 0
PERI_MS_PPU_FX314_MS_ATT1	0x400256B4	FULL	Master attributes 1
PERI_MS_PPU_FX314_MS_ATT2	0x400256B8	FULL	Master attributes 2
PERI_MS_PPU_FX314_MS_ATT3	0x400256BC	FULL	Master attributes 3

21.332 PPU_FX 315

Register Name	Address	Permission	Description
PERI_MS_PPU_FX315_SL_ADDR	0x400256C0	FULL	Slave region, base address
PERI_MS_PPU_FX315_SL_SIZE	0x400256C4	FULL	Slave region, size
PERI_MS_PPU_FX315_SL_ATT0	0x400256D0	FULL	Slave attributes 0
PERI_MS_PPU_FX315_SL_ATT1	0x400256D4	FULL	Slave attributes 1
PERI_MS_PPU_FX315_SL_ATT2	0x400256D8	FULL	Slave attributes 2
PERI_MS_PPU_FX315_SL_ATT3	0x400256DC	FULL	Slave attributes 3
PERI_MS_PPU_FX315_MS_ADDR	0x400256E0	FULL	Master region, base address
PERI_MS_PPU_FX315_MS_SIZE	0x400256E4	FULL	Master region, size
PERI_MS_PPU_FX315_MS_ATT0	0x400256F0	FULL	Master attributes 0
PERI_MS_PPU_FX315_MS_ATT1	0x400256F4	FULL	Master attributes 1
PERI_MS_PPU_FX315_MS_ATT2	0x400256F8	FULL	Master attributes 2
PERI_MS_PPU_FX315_MS_ATT3	0x400256FC	FULL	Master attributes 3

21.333 PPU_FX 316

Register Name	Address	Permission	Description
PERI_MS_PPU_FX316_SL_ADDR	0x40025700	FULL	Slave region, base address
PERI_MS_PPU_FX316_SL_SIZE	0x40025704	FULL	Slave region, size
PERI_MS_PPU_FX316_SL_ATT0	0x40025710	FULL	Slave attributes 0
PERI_MS_PPU_FX316_SL_ATT1	0x40025714	FULL	Slave attributes 1
PERI_MS_PPU_FX316_SL_ATT2	0x40025718	FULL	Slave attributes 2
PERI_MS_PPU_FX316_SL_ATT3	0x4002571C	FULL	Slave attributes 3
PERI_MS_PPU_FX316_MS_ADDR	0x40025720	FULL	Master region, base address
PERI_MS_PPU_FX316_MS_SIZE	0x40025724	FULL	Master region, size
PERI_MS_PPU_FX316_MS_ATT0	0x40025730	FULL	Master attributes 0
PERI_MS_PPU_FX316_MS_ATT1	0x40025734	FULL	Master attributes 1
PERI_MS_PPU_FX316_MS_ATT2	0x40025738	FULL	Master attributes 2
PERI_MS_PPU_FX316_MS_ATT3	0x4002573C	FULL	Master attributes 3

21.334 PPU_FX 317

Register Name	Address	Permission	Description
PERI_MS_PPU_FX317_SL_ADDR	0x40025740	FULL	Slave region, base address
PERI_MS_PPU_FX317_SL_SIZE	0x40025744	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX317_SL_ATT0	0x40025750	FULL	Slave attributes 0
PERI_MS_PPU_FX317_SL_ATT1	0x40025754	FULL	Slave attributes 1
PERI_MS_PPU_FX317_SL_ATT2	0x40025758	FULL	Slave attributes 2
PERI_MS_PPU_FX317_SL_ATT3	0x4002575C	FULL	Slave attributes 3
PERI_MS_PPU_FX317_MS_ADDR	0x40025760	FULL	Master region, base address
PERI_MS_PPU_FX317_MS_SIZE	0x40025764	FULL	Master region, size
PERI_MS_PPU_FX317_MS_ATT0	0x40025770	FULL	Master attributes 0
PERI_MS_PPU_FX317_MS_ATT1	0x40025774	FULL	Master attributes 1
PERI_MS_PPU_FX317_MS_ATT2	0x40025778	FULL	Master attributes 2
PERI_MS_PPU_FX317_MS_ATT3	0x4002577C	FULL	Master attributes 3

21.335 PPU_FX 318

Register Name	Address	Permission	Description
PERI_MS_PPU_FX318_SL_ADDR	0x40025780	FULL	Slave region, base address
PERI_MS_PPU_FX318_SL_SIZE	0x40025784	FULL	Slave region, size
PERI_MS_PPU_FX318_SL_ATT0	0x40025790	FULL	Slave attributes 0
PERI_MS_PPU_FX318_SL_ATT1	0x40025794	FULL	Slave attributes 1
PERI_MS_PPU_FX318_SL_ATT2	0x40025798	FULL	Slave attributes 2
PERI_MS_PPU_FX318_SL_ATT3	0x4002579C	FULL	Slave attributes 3
PERI_MS_PPU_FX318_MS_ADDR	0x400257A0	FULL	Master region, base address
PERI_MS_PPU_FX318_MS_SIZE	0x400257A4	FULL	Master region, size
PERI_MS_PPU_FX318_MS_ATT0	0x400257B0	FULL	Master attributes 0
PERI_MS_PPU_FX318_MS_ATT1	0x400257B4	FULL	Master attributes 1
PERI_MS_PPU_FX318_MS_ATT2	0x400257B8	FULL	Master attributes 2
PERI_MS_PPU_FX318_MS_ATT3	0x400257BC	FULL	Master attributes 3

21.336 PPU_FX 319

Register Name	Address	Permission	Description
PERI_MS_PPU_FX319_SL_ADDR	0x400257C0	FULL	Slave region, base address
PERI_MS_PPU_FX319_SL_SIZE	0x400257C4	FULL	Slave region, size
PERI_MS_PPU_FX319_SL_ATT0	0x400257D0	FULL	Slave attributes 0
PERI_MS_PPU_FX319_SL_ATT1	0x400257D4	FULL	Slave attributes 1
PERI_MS_PPU_FX319_SL_ATT2	0x400257D8	FULL	Slave attributes 2
PERI_MS_PPU_FX319_SL_ATT3	0x400257DC	FULL	Slave attributes 3
PERI_MS_PPU_FX319_MS_ADDR	0x400257E0	FULL	Master region, base address
PERI_MS_PPU_FX319_MS_SIZE	0x400257E4	FULL	Master region, size
PERI_MS_PPU_FX319_MS_ATT0	0x400257F0	FULL	Master attributes 0
PERI_MS_PPU_FX319_MS_ATT1	0x400257F4	FULL	Master attributes 1
PERI_MS_PPU_FX319_MS_ATT2	0x400257F8	FULL	Master attributes 2
PERI_MS_PPU_FX319_MS_ATT3	0x400257FC	FULL	Master attributes 3

21.337 PPU_FX 320

Register Name	Address	Permission	Description
PERI_MS_PPU_FX320_SL_ADDR	0x40025800	FULL	Slave region, base address
PERI_MS_PPU_FX320_SL_SIZE	0x40025804	FULL	Slave region, size
PERI_MS_PPU_FX320_SL_ATT0	0x40025810	FULL	Slave attributes 0
PERI_MS_PPU_FX320_SL_ATT1	0x40025814	FULL	Slave attributes 1
PERI_MS_PPU_FX320_SL_ATT2	0x40025818	FULL	Slave attributes 2
PERI_MS_PPU_FX320_SL_ATT3	0x4002581C	FULL	Slave attributes 3
PERI_MS_PPU_FX320_MS_ADDR	0x40025820	FULL	Master region, base address
PERI_MS_PPU_FX320_MS_SIZE	0x40025824	FULL	Master region, size
PERI_MS_PPU_FX320_MS_ATT0	0x40025830	FULL	Master attributes 0
PERI_MS_PPU_FX320_MS_ATT1	0x40025834	FULL	Master attributes 1
PERI_MS_PPU_FX320_MS_ATT2	0x40025838	FULL	Master attributes 2
PERI_MS_PPU_FX320_MS_ATT3	0x4002583C	FULL	Master attributes 3

21.338 PPU_FX 321

Register Name	Address	Permission	Description
PERI_MS_PPU_FX321_SL_ADDR	0x40025840	FULL	Slave region, base address
PERI_MS_PPU_FX321_SL_SIZE	0x40025844	FULL	Slave region, size
PERI_MS_PPU_FX321_SL_ATT0	0x40025850	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX321_SL_ATT1	0x40025854	FULL	Slave attributes 1
PERI_MS_PPU_FX321_SL_ATT2	0x40025858	FULL	Slave attributes 2
PERI_MS_PPU_FX321_SL_ATT3	0x4002585C	FULL	Slave attributes 3
PERI_MS_PPU_FX321_MS_ADDR	0x40025860	FULL	Master region, base address
PERI_MS_PPU_FX321_MS_SIZE	0x40025864	FULL	Master region, size
PERI_MS_PPU_FX321_MS_ATT0	0x40025870	FULL	Master attributes 0
PERI_MS_PPU_FX321_MS_ATT1	0x40025874	FULL	Master attributes 1
PERI_MS_PPU_FX321_MS_ATT2	0x40025878	FULL	Master attributes 2
PERI_MS_PPU_FX321_MS_ATT3	0x4002587C	FULL	Master attributes 3

21.339 PPU_FX 322

Register Name	Address	Permission	Description
PERI_MS_PPU_FX322_SL_ADDR	0x40025880	FULL	Slave region, base address
PERI_MS_PPU_FX322_SL_SIZE	0x40025884	FULL	Slave region, size
PERI_MS_PPU_FX322_SL_ATT0	0x40025890	FULL	Slave attributes 0
PERI_MS_PPU_FX322_SL_ATT1	0x40025894	FULL	Slave attributes 1
PERI_MS_PPU_FX322_SL_ATT2	0x40025898	FULL	Slave attributes 2
PERI_MS_PPU_FX322_SL_ATT3	0x4002589C	FULL	Slave attributes 3
PERI_MS_PPU_FX322_MS_ADDR	0x400258A0	FULL	Master region, base address
PERI_MS_PPU_FX322_MS_SIZE	0x400258A4	FULL	Master region, size
PERI_MS_PPU_FX322_MS_ATT0	0x400258B0	FULL	Master attributes 0
PERI_MS_PPU_FX322_MS_ATT1	0x400258B4	FULL	Master attributes 1
PERI_MS_PPU_FX322_MS_ATT2	0x400258B8	FULL	Master attributes 2
PERI_MS_PPU_FX322_MS_ATT3	0x400258BC	FULL	Master attributes 3

21.340 PPU_FX 323

Register Name	Address	Permission	Description
PERI_MS_PPU_FX323_SL_ADDR	0x400258C0	FULL	Slave region, base address
PERI_MS_PPU_FX323_SL_SIZE	0x400258C4	FULL	Slave region, size
PERI_MS_PPU_FX323_SL_ATT0	0x400258D0	FULL	Slave attributes 0
PERI_MS_PPU_FX323_SL_ATT1	0x400258D4	FULL	Slave attributes 1
PERI_MS_PPU_FX323_SL_ATT2	0x400258D8	FULL	Slave attributes 2
PERI_MS_PPU_FX323_SL_ATT3	0x400258DC	FULL	Slave attributes 3
PERI_MS_PPU_FX323_MS_ADDR	0x400258E0	FULL	Master region, base address
PERI_MS_PPU_FX323_MS_SIZE	0x400258E4	FULL	Master region, size
PERI_MS_PPU_FX323_MS_ATT0	0x400258F0	FULL	Master attributes 0
PERI_MS_PPU_FX323_MS_ATT1	0x400258F4	FULL	Master attributes 1
PERI_MS_PPU_FX323_MS_ATT2	0x400258F8	FULL	Master attributes 2
PERI_MS_PPU_FX323_MS_ATT3	0x400258FC	FULL	Master attributes 3

21.341 PPU_FX 324

Register Name	Address	Permission	Description
PERI_MS_PPU_FX324_SL_ADDR	0x40025900	FULL	Slave region, base address
PERI_MS_PPU_FX324_SL_SIZE	0x40025904	FULL	Slave region, size
PERI_MS_PPU_FX324_SL_ATT0	0x40025910	FULL	Slave attributes 0
PERI_MS_PPU_FX324_SL_ATT1	0x40025914	FULL	Slave attributes 1
PERI_MS_PPU_FX324_SL_ATT2	0x40025918	FULL	Slave attributes 2
PERI_MS_PPU_FX324_SL_ATT3	0x4002591C	FULL	Slave attributes 3
PERI_MS_PPU_FX324_MS_ADDR	0x40025920	FULL	Master region, base address
PERI_MS_PPU_FX324_MS_SIZE	0x40025924	FULL	Master region, size
PERI_MS_PPU_FX324_MS_ATT0	0x40025930	FULL	Master attributes 0
PERI_MS_PPU_FX324_MS_ATT1	0x40025934	FULL	Master attributes 1
PERI_MS_PPU_FX324_MS_ATT2	0x40025938	FULL	Master attributes 2
PERI_MS_PPU_FX324_MS_ATT3	0x4002593C	FULL	Master attributes 3

21.342 PPU_FX 325

Register Name	Address	Permission	Description
PERI_MS_PPU_FX325_SL_ADDR	0x40025940	FULL	Slave region, base address
PERI_MS_PPU_FX325_SL_SIZE	0x40025944	FULL	Slave region, size
PERI_MS_PPU_FX325_SL_ATT0	0x40025950	FULL	Slave attributes 0
PERI_MS_PPU_FX325_SL_ATT1	0x40025954	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX325_SL_ATT2	0x40025958	FULL	Slave attributes 2
PERI_MS_PPU_FX325_SL_ATT3	0x4002595C	FULL	Slave attributes 3
PERI_MS_PPU_FX325_MS_ADDR	0x40025960	FULL	Master region, base address
PERI_MS_PPU_FX325_MS_SIZE	0x40025964	FULL	Master region, size
PERI_MS_PPU_FX325_MS_ATT0	0x40025970	FULL	Master attributes 0
PERI_MS_PPU_FX325_MS_ATT1	0x40025974	FULL	Master attributes 1
PERI_MS_PPU_FX325_MS_ATT2	0x40025978	FULL	Master attributes 2
PERI_MS_PPU_FX325_MS_ATT3	0x4002597C	FULL	Master attributes 3

21.343 PPU_FX 326

Register Name	Address	Permission	Description
PERI_MS_PPU_FX326_SL_ADDR	0x40025980	FULL	Slave region, base address
PERI_MS_PPU_FX326_SL_SIZE	0x40025984	FULL	Slave region, size
PERI_MS_PPU_FX326_SL_ATT0	0x40025990	FULL	Slave attributes 0
PERI_MS_PPU_FX326_SL_ATT1	0x40025994	FULL	Slave attributes 1
PERI_MS_PPU_FX326_SL_ATT2	0x40025998	FULL	Slave attributes 2
PERI_MS_PPU_FX326_SL_ATT3	0x4002599C	FULL	Slave attributes 3
PERI_MS_PPU_FX326_MS_ADDR	0x400259A0	FULL	Master region, base address
PERI_MS_PPU_FX326_MS_SIZE	0x400259A4	FULL	Master region, size
PERI_MS_PPU_FX326_MS_ATT0	0x400259B0	FULL	Master attributes 0
PERI_MS_PPU_FX326_MS_ATT1	0x400259B4	FULL	Master attributes 1
PERI_MS_PPU_FX326_MS_ATT2	0x400259B8	FULL	Master attributes 2
PERI_MS_PPU_FX326_MS_ATT3	0x400259BC	FULL	Master attributes 3

21.344 PPU_FX 327

Register Name	Address	Permission	Description
PERI_MS_PPU_FX327_SL_ADDR	0x400259C0	FULL	Slave region, base address
PERI_MS_PPU_FX327_SL_SIZE	0x400259C4	FULL	Slave region, size
PERI_MS_PPU_FX327_SL_ATT0	0x400259D0	FULL	Slave attributes 0
PERI_MS_PPU_FX327_SL_ATT1	0x400259D4	FULL	Slave attributes 1
PERI_MS_PPU_FX327_SL_ATT2	0x400259D8	FULL	Slave attributes 2
PERI_MS_PPU_FX327_SL_ATT3	0x400259DC	FULL	Slave attributes 3
PERI_MS_PPU_FX327_MS_ADDR	0x400259E0	FULL	Master region, base address
PERI_MS_PPU_FX327_MS_SIZE	0x400259E4	FULL	Master region, size
PERI_MS_PPU_FX327_MS_ATT0	0x400259F0	FULL	Master attributes 0
PERI_MS_PPU_FX327_MS_ATT1	0x400259F4	FULL	Master attributes 1
PERI_MS_PPU_FX327_MS_ATT2	0x400259F8	FULL	Master attributes 2
PERI_MS_PPU_FX327_MS_ATT3	0x400259FC	FULL	Master attributes 3

21.345 PPU_FX 328

Register Name	Address	Permission	Description
PERI_MS_PPU_FX328_SL_ADDR	0x40025A00	FULL	Slave region, base address
PERI_MS_PPU_FX328_SL_SIZE	0x40025A04	FULL	Slave region, size
PERI_MS_PPU_FX328_SL_ATT0	0x40025A10	FULL	Slave attributes 0
PERI_MS_PPU_FX328_SL_ATT1	0x40025A14	FULL	Slave attributes 1
PERI_MS_PPU_FX328_SL_ATT2	0x40025A18	FULL	Slave attributes 2
PERI_MS_PPU_FX328_SL_ATT3	0x40025A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX328_MS_ADDR	0x40025A20	FULL	Master region, base address
PERI_MS_PPU_FX328_MS_SIZE	0x40025A24	FULL	Master region, size
PERI_MS_PPU_FX328_MS_ATT0	0x40025A30	FULL	Master attributes 0
PERI_MS_PPU_FX328_MS_ATT1	0x40025A34	FULL	Master attributes 1
PERI_MS_PPU_FX328_MS_ATT2	0x40025A38	FULL	Master attributes 2
PERI_MS_PPU_FX328_MS_ATT3	0x40025A3C	FULL	Master attributes 3

21.346 PPU_FX 329

Register Name	Address	Permission	Description
PERI_MS_PPU_FX329_SL_ADDR	0x40025A40	FULL	Slave region, base address
PERI_MS_PPU_FX329_SL_SIZE	0x40025A44	FULL	Slave region, size
PERI_MS_PPU_FX329_SL_ATT0	0x40025A50	FULL	Slave attributes 0
PERI_MS_PPU_FX329_SL_ATT1	0x40025A54	FULL	Slave attributes 1
PERI_MS_PPU_FX329_SL_ATT2	0x40025A58	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX329_SL_ATT3	0x40025A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX329_MS_ADDR	0x40025A60	FULL	Master region, base address
PERI_MS_PPU_FX329_MS_SIZE	0x40025A64	FULL	Master region, size
PERI_MS_PPU_FX329_MS_ATT0	0x40025A70	FULL	Master attributes 0
PERI_MS_PPU_FX329_MS_ATT1	0x40025A74	FULL	Master attributes 1
PERI_MS_PPU_FX329_MS_ATT2	0x40025A78	FULL	Master attributes 2
PERI_MS_PPU_FX329_MS_ATT3	0x40025A7C	FULL	Master attributes 3

21.347 PPU_FX 330

Register Name	Address	Permission	Description
PERI_MS_PPU_FX330_SL_ADDR	0x40025A80	FULL	Slave region, base address
PERI_MS_PPU_FX330_SL_SIZE	0x40025A84	FULL	Slave region, size
PERI_MS_PPU_FX330_SL_ATT0	0x40025A90	FULL	Slave attributes 0
PERI_MS_PPU_FX330_SL_ATT1	0x40025A94	FULL	Slave attributes 1
PERI_MS_PPU_FX330_SL_ATT2	0x40025A98	FULL	Slave attributes 2
PERI_MS_PPU_FX330_SL_ATT3	0x40025A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX330_MS_ADDR	0x40025AA0	FULL	Master region, base address
PERI_MS_PPU_FX330_MS_SIZE	0x40025AA4	FULL	Master region, size
PERI_MS_PPU_FX330_MS_ATT0	0x40025AB0	FULL	Master attributes 0
PERI_MS_PPU_FX330_MS_ATT1	0x40025AB4	FULL	Master attributes 1
PERI_MS_PPU_FX330_MS_ATT2	0x40025AB8	FULL	Master attributes 2
PERI_MS_PPU_FX330_MS_ATT3	0x40025ABC	FULL	Master attributes 3

21.348 PPU_FX 331

Register Name	Address	Permission	Description
PERI_MS_PPU_FX331_SL_ADDR	0x40025AC0	FULL	Slave region, base address
PERI_MS_PPU_FX331_SL_SIZE	0x40025AC4	FULL	Slave region, size
PERI_MS_PPU_FX331_SL_ATT0	0x40025AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX331_SL_ATT1	0x40025AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX331_SL_ATT2	0x40025AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX331_SL_ATT3	0x40025ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX331_MS_ADDR	0x40025AE0	FULL	Master region, base address
PERI_MS_PPU_FX331_MS_SIZE	0x40025AE4	FULL	Master region, size
PERI_MS_PPU_FX331_MS_ATT0	0x40025AF0	FULL	Master attributes 0
PERI_MS_PPU_FX331_MS_ATT1	0x40025AF4	FULL	Master attributes 1
PERI_MS_PPU_FX331_MS_ATT2	0x40025AF8	FULL	Master attributes 2
PERI_MS_PPU_FX331_MS_ATT3	0x40025AFC	FULL	Master attributes 3

21.349 PPU_FX 332

Register Name	Address	Permission	Description
PERI_MS_PPU_FX332_SL_ADDR	0x40025B00	FULL	Slave region, base address
PERI_MS_PPU_FX332_SL_SIZE	0x40025B04	FULL	Slave region, size
PERI_MS_PPU_FX332_SL_ATT0	0x40025B10	FULL	Slave attributes 0
PERI_MS_PPU_FX332_SL_ATT1	0x40025B14	FULL	Slave attributes 1
PERI_MS_PPU_FX332_SL_ATT2	0x40025B18	FULL	Slave attributes 2
PERI_MS_PPU_FX332_SL_ATT3	0x40025B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX332_MS_ADDR	0x40025B20	FULL	Master region, base address
PERI_MS_PPU_FX332_MS_SIZE	0x40025B24	FULL	Master region, size
PERI_MS_PPU_FX332_MS_ATT0	0x40025B30	FULL	Master attributes 0
PERI_MS_PPU_FX332_MS_ATT1	0x40025B34	FULL	Master attributes 1
PERI_MS_PPU_FX332_MS_ATT2	0x40025B38	FULL	Master attributes 2
PERI_MS_PPU_FX332_MS_ATT3	0x40025B3C	FULL	Master attributes 3

21.350 PPU_FX 333

Register Name	Address	Permission	Description
PERI_MS_PPU_FX333_SL_ADDR	0x40025B40	FULL	Slave region, base address
PERI_MS_PPU_FX333_SL_SIZE	0x40025B44	FULL	Slave region, size
PERI_MS_PPU_FX333_SL_ATT0	0x40025B50	FULL	Slave attributes 0
PERI_MS_PPU_FX333_SL_ATT1	0x40025B54	FULL	Slave attributes 1
PERI_MS_PPU_FX333_SL_ATT2	0x40025B58	FULL	Slave attributes 2
PERI_MS_PPU_FX333_SL_ATT3	0x40025B5C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX333_MS_ADDR	0x40025B60	FULL	Master region, base address
PERI_MS_PPU_FX333_MS_SIZE	0x40025B64	FULL	Master region, size
PERI_MS_PPU_FX333_MS_ATT0	0x40025B70	FULL	Master attributes 0
PERI_MS_PPU_FX333_MS_ATT1	0x40025B74	FULL	Master attributes 1
PERI_MS_PPU_FX333_MS_ATT2	0x40025B78	FULL	Master attributes 2
PERI_MS_PPU_FX333_MS_ATT3	0x40025B7C	FULL	Master attributes 3

21.351 PPU_FX 334

Register Name	Address	Permission	Description
PERI_MS_PPU_FX334_SL_ADDR	0x40025B80	FULL	Slave region, base address
PERI_MS_PPU_FX334_SL_SIZE	0x40025B84	FULL	Slave region, size
PERI_MS_PPU_FX334_SL_ATT0	0x40025B90	FULL	Slave attributes 0
PERI_MS_PPU_FX334_SL_ATT1	0x40025B94	FULL	Slave attributes 1
PERI_MS_PPU_FX334_SL_ATT2	0x40025B98	FULL	Slave attributes 2
PERI_MS_PPU_FX334_SL_ATT3	0x40025B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX334_MS_ADDR	0x40025BA0	FULL	Master region, base address
PERI_MS_PPU_FX334_MS_SIZE	0x40025BA4	FULL	Master region, size
PERI_MS_PPU_FX334_MS_ATT0	0x40025BB0	FULL	Master attributes 0
PERI_MS_PPU_FX334_MS_ATT1	0x40025BB4	FULL	Master attributes 1
PERI_MS_PPU_FX334_MS_ATT2	0x40025BB8	FULL	Master attributes 2
PERI_MS_PPU_FX334_MS_ATT3	0x40025BBC	FULL	Master attributes 3

21.352 PPU_FX 335

Register Name	Address	Permission	Description
PERI_MS_PPU_FX335_SL_ADDR	0x40025BC0	FULL	Slave region, base address
PERI_MS_PPU_FX335_SL_SIZE	0x40025BC4	FULL	Slave region, size
PERI_MS_PPU_FX335_SL_ATT0	0x40025BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX335_SL_ATT1	0x40025BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX335_SL_ATT2	0x40025BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX335_SL_ATT3	0x40025BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX335_MS_ADDR	0x40025BE0	FULL	Master region, base address
PERI_MS_PPU_FX335_MS_SIZE	0x40025BE4	FULL	Master region, size
PERI_MS_PPU_FX335_MS_ATT0	0x40025BF0	FULL	Master attributes 0
PERI_MS_PPU_FX335_MS_ATT1	0x40025BF4	FULL	Master attributes 1
PERI_MS_PPU_FX335_MS_ATT2	0x40025BF8	FULL	Master attributes 2
PERI_MS_PPU_FX335_MS_ATT3	0x40025BFC	FULL	Master attributes 3

21.353 PPU_FX 336

Register Name	Address	Permission	Description
PERI_MS_PPU_FX336_SL_ADDR	0x40025C00	FULL	Slave region, base address
PERI_MS_PPU_FX336_SL_SIZE	0x40025C04	FULL	Slave region, size
PERI_MS_PPU_FX336_SL_ATT0	0x40025C10	FULL	Slave attributes 0
PERI_MS_PPU_FX336_SL_ATT1	0x40025C14	FULL	Slave attributes 1
PERI_MS_PPU_FX336_SL_ATT2	0x40025C18	FULL	Slave attributes 2
PERI_MS_PPU_FX336_SL_ATT3	0x40025C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX336_MS_ADDR	0x40025C20	FULL	Master region, base address
PERI_MS_PPU_FX336_MS_SIZE	0x40025C24	FULL	Master region, size
PERI_MS_PPU_FX336_MS_ATT0	0x40025C30	FULL	Master attributes 0
PERI_MS_PPU_FX336_MS_ATT1	0x40025C34	FULL	Master attributes 1
PERI_MS_PPU_FX336_MS_ATT2	0x40025C38	FULL	Master attributes 2
PERI_MS_PPU_FX336_MS_ATT3	0x40025C3C	FULL	Master attributes 3

21.354 PPU_FX 337

Register Name	Address	Permission	Description
PERI_MS_PPU_FX337_SL_ADDR	0x40025C40	FULL	Slave region, base address
PERI_MS_PPU_FX337_SL_SIZE	0x40025C44	FULL	Slave region, size
PERI_MS_PPU_FX337_SL_ATT0	0x40025C50	FULL	Slave attributes 0
PERI_MS_PPU_FX337_SL_ATT1	0x40025C54	FULL	Slave attributes 1
PERI_MS_PPU_FX337_SL_ATT2	0x40025C58	FULL	Slave attributes 2
PERI_MS_PPU_FX337_SL_ATT3	0x40025C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX337_MS_ADDR	0x40025C60	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX337_MS_SIZE	0x40025C64	FULL	Master region, size
PERI_MS_PPU_FX337_MS_ATT0	0x40025C70	FULL	Master attributes 0
PERI_MS_PPU_FX337_MS_ATT1	0x40025C74	FULL	Master attributes 1
PERI_MS_PPU_FX337_MS_ATT2	0x40025C78	FULL	Master attributes 2
PERI_MS_PPU_FX337_MS_ATT3	0x40025C7C	FULL	Master attributes 3

21.355 PPU_FX 338

Register Name	Address	Permission	Description
PERI_MS_PPU_FX338_SL_ADDR	0x40025C80	FULL	Slave region, base address
PERI_MS_PPU_FX338_SL_SIZE	0x40025C84	FULL	Slave region, size
PERI_MS_PPU_FX338_SL_ATT0	0x40025C90	FULL	Slave attributes 0
PERI_MS_PPU_FX338_SL_ATT1	0x40025C94	FULL	Slave attributes 1
PERI_MS_PPU_FX338_SL_ATT2	0x40025C98	FULL	Slave attributes 2
PERI_MS_PPU_FX338_SL_ATT3	0x40025C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX338_MS_ADDR	0x40025CA0	FULL	Master region, base address
PERI_MS_PPU_FX338_MS_SIZE	0x40025CA4	FULL	Master region, size
PERI_MS_PPU_FX338_MS_ATT0	0x40025CB0	FULL	Master attributes 0
PERI_MS_PPU_FX338_MS_ATT1	0x40025CB4	FULL	Master attributes 1
PERI_MS_PPU_FX338_MS_ATT2	0x40025CB8	FULL	Master attributes 2
PERI_MS_PPU_FX338_MS_ATT3	0x40025CBC	FULL	Master attributes 3

21.356 PPU_FX 339

Register Name	Address	Permission	Description
PERI_MS_PPU_FX339_SL_ADDR	0x40025CC0	FULL	Slave region, base address
PERI_MS_PPU_FX339_SL_SIZE	0x40025CC4	FULL	Slave region, size
PERI_MS_PPU_FX339_SL_ATT0	0x40025CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX339_SL_ATT1	0x40025CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX339_SL_ATT2	0x40025CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX339_SL_ATT3	0x40025CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX339_MS_ADDR	0x40025CE0	FULL	Master region, base address
PERI_MS_PPU_FX339_MS_SIZE	0x40025CE4	FULL	Master region, size
PERI_MS_PPU_FX339_MS_ATT0	0x40025CF0	FULL	Master attributes 0
PERI_MS_PPU_FX339_MS_ATT1	0x40025CF4	FULL	Master attributes 1
PERI_MS_PPU_FX339_MS_ATT2	0x40025CF8	FULL	Master attributes 2
PERI_MS_PPU_FX339_MS_ATT3	0x40025CFC	FULL	Master attributes 3

21.357 PPU_FX 340

Register Name	Address	Permission	Description
PERI_MS_PPU_FX340_SL_ADDR	0x40025D00	FULL	Slave region, base address
PERI_MS_PPU_FX340_SL_SIZE	0x40025D04	FULL	Slave region, size
PERI_MS_PPU_FX340_SL_ATT0	0x40025D10	FULL	Slave attributes 0
PERI_MS_PPU_FX340_SL_ATT1	0x40025D14	FULL	Slave attributes 1
PERI_MS_PPU_FX340_SL_ATT2	0x40025D18	FULL	Slave attributes 2
PERI_MS_PPU_FX340_SL_ATT3	0x40025D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX340_MS_ADDR	0x40025D20	FULL	Master region, base address
PERI_MS_PPU_FX340_MS_SIZE	0x40025D24	FULL	Master region, size
PERI_MS_PPU_FX340_MS_ATT0	0x40025D30	FULL	Master attributes 0
PERI_MS_PPU_FX340_MS_ATT1	0x40025D34	FULL	Master attributes 1
PERI_MS_PPU_FX340_MS_ATT2	0x40025D38	FULL	Master attributes 2
PERI_MS_PPU_FX340_MS_ATT3	0x40025D3C	FULL	Master attributes 3

21.358 PPU_FX 341

Register Name	Address	Permission	Description
PERI_MS_PPU_FX341_SL_ADDR	0x40025D40	FULL	Slave region, base address
PERI_MS_PPU_FX341_SL_SIZE	0x40025D44	FULL	Slave region, size
PERI_MS_PPU_FX341_SL_ATT0	0x40025D50	FULL	Slave attributes 0
PERI_MS_PPU_FX341_SL_ATT1	0x40025D54	FULL	Slave attributes 1
PERI_MS_PPU_FX341_SL_ATT2	0x40025D58	FULL	Slave attributes 2
PERI_MS_PPU_FX341_SL_ATT3	0x40025D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX341_MS_ADDR	0x40025D60	FULL	Master region, base address
PERI_MS_PPU_FX341_MS_SIZE	0x40025D64	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX341_MS_ATT0	0x40025D70	FULL	Master attributes 0
PERI_MS_PPU_FX341_MS_ATT1	0x40025D74	FULL	Master attributes 1
PERI_MS_PPU_FX341_MS_ATT2	0x40025D78	FULL	Master attributes 2
PERI_MS_PPU_FX341_MS_ATT3	0x40025D7C	FULL	Master attributes 3

21.359 PPU_FX 342

Register Name	Address	Permission	Description
PERI_MS_PPU_FX342_SL_ADDR	0x40025D80	FULL	Slave region, base address
PERI_MS_PPU_FX342_SL_SIZE	0x40025D84	FULL	Slave region, size
PERI_MS_PPU_FX342_SL_ATT0	0x40025D90	FULL	Slave attributes 0
PERI_MS_PPU_FX342_SL_ATT1	0x40025D94	FULL	Slave attributes 1
PERI_MS_PPU_FX342_SL_ATT2	0x40025D98	FULL	Slave attributes 2
PERI_MS_PPU_FX342_SL_ATT3	0x40025D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX342_MS_ADDR	0x40025DA0	FULL	Master region, base address
PERI_MS_PPU_FX342_MS_SIZE	0x40025DA4	FULL	Master region, size
PERI_MS_PPU_FX342_MS_ATT0	0x40025DB0	FULL	Master attributes 0
PERI_MS_PPU_FX342_MS_ATT1	0x40025DB4	FULL	Master attributes 1
PERI_MS_PPU_FX342_MS_ATT2	0x40025DB8	FULL	Master attributes 2
PERI_MS_PPU_FX342_MS_ATT3	0x40025DBC	FULL	Master attributes 3

21.360 PPU_FX 343

Register Name	Address	Permission	Description
PERI_MS_PPU_FX343_SL_ADDR	0x40025DC0	FULL	Slave region, base address
PERI_MS_PPU_FX343_SL_SIZE	0x40025DC4	FULL	Slave region, size
PERI_MS_PPU_FX343_SL_ATT0	0x40025DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX343_SL_ATT1	0x40025DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX343_SL_ATT2	0x40025DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX343_SL_ATT3	0x40025DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX343_MS_ADDR	0x40025DE0	FULL	Master region, base address
PERI_MS_PPU_FX343_MS_SIZE	0x40025DE4	FULL	Master region, size
PERI_MS_PPU_FX343_MS_ATT0	0x40025DF0	FULL	Master attributes 0
PERI_MS_PPU_FX343_MS_ATT1	0x40025DF4	FULL	Master attributes 1
PERI_MS_PPU_FX343_MS_ATT2	0x40025DF8	FULL	Master attributes 2
PERI_MS_PPU_FX343_MS_ATT3	0x40025DFC	FULL	Master attributes 3

21.361 PPU_FX 344

Register Name	Address	Permission	Description
PERI_MS_PPU_FX344_SL_ADDR	0x40025E00	FULL	Slave region, base address
PERI_MS_PPU_FX344_SL_SIZE	0x40025E04	FULL	Slave region, size
PERI_MS_PPU_FX344_SL_ATT0	0x40025E10	FULL	Slave attributes 0
PERI_MS_PPU_FX344_SL_ATT1	0x40025E14	FULL	Slave attributes 1
PERI_MS_PPU_FX344_SL_ATT2	0x40025E18	FULL	Slave attributes 2
PERI_MS_PPU_FX344_SL_ATT3	0x40025E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX344_MS_ADDR	0x40025E20	FULL	Master region, base address
PERI_MS_PPU_FX344_MS_SIZE	0x40025E24	FULL	Master region, size
PERI_MS_PPU_FX344_MS_ATT0	0x40025E30	FULL	Master attributes 0
PERI_MS_PPU_FX344_MS_ATT1	0x40025E34	FULL	Master attributes 1
PERI_MS_PPU_FX344_MS_ATT2	0x40025E38	FULL	Master attributes 2
PERI_MS_PPU_FX344_MS_ATT3	0x40025E3C	FULL	Master attributes 3

21.362 PPU_FX 345

Register Name	Address	Permission	Description
PERI_MS_PPU_FX345_SL_ADDR	0x40025E40	FULL	Slave region, base address
PERI_MS_PPU_FX345_SL_SIZE	0x40025E44	FULL	Slave region, size
PERI_MS_PPU_FX345_SL_ATT0	0x40025E50	FULL	Slave attributes 0
PERI_MS_PPU_FX345_SL_ATT1	0x40025E54	FULL	Slave attributes 1
PERI_MS_PPU_FX345_SL_ATT2	0x40025E58	FULL	Slave attributes 2
PERI_MS_PPU_FX345_SL_ATT3	0x40025E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX345_MS_ADDR	0x40025E60	FULL	Master region, base address
PERI_MS_PPU_FX345_MS_SIZE	0x40025E64	FULL	Master region, size
PERI_MS_PPU_FX345_MS_ATT0	0x40025E70	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX345_MS_ATT1	0x40025E74	FULL	Master attributes 1
PERI_MS_PPU_FX345_MS_ATT2	0x40025E78	FULL	Master attributes 2
PERI_MS_PPU_FX345_MS_ATT3	0x40025E7C	FULL	Master attributes 3

21.363 PPU_FX 346

Register Name	Address	Permission	Description
PERI_MS_PPU_FX346_SL_ADDR	0x40025E80	FULL	Slave region, base address
PERI_MS_PPU_FX346_SL_SIZE	0x40025E84	FULL	Slave region, size
PERI_MS_PPU_FX346_SL_ATT0	0x40025E90	FULL	Slave attributes 0
PERI_MS_PPU_FX346_SL_ATT1	0x40025E94	FULL	Slave attributes 1
PERI_MS_PPU_FX346_SL_ATT2	0x40025E98	FULL	Slave attributes 2
PERI_MS_PPU_FX346_SL_ATT3	0x40025E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX346_MS_ADDR	0x40025EA0	FULL	Master region, base address
PERI_MS_PPU_FX346_MS_SIZE	0x40025EA4	FULL	Master region, size
PERI_MS_PPU_FX346_MS_ATT0	0x40025EB0	FULL	Master attributes 0
PERI_MS_PPU_FX346_MS_ATT1	0x40025EB4	FULL	Master attributes 1
PERI_MS_PPU_FX346_MS_ATT2	0x40025EB8	FULL	Master attributes 2
PERI_MS_PPU_FX346_MS_ATT3	0x40025EBC	FULL	Master attributes 3

21.364 PPU_FX 347

Register Name	Address	Permission	Description
PERI_MS_PPU_FX347_SL_ADDR	0x40025EC0	FULL	Slave region, base address
PERI_MS_PPU_FX347_SL_SIZE	0x40025EC4	FULL	Slave region, size
PERI_MS_PPU_FX347_SL_ATT0	0x40025ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX347_SL_ATT1	0x40025ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX347_SL_ATT2	0x40025ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX347_SL_ATT3	0x40025EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX347_MS_ADDR	0x40025EE0	FULL	Master region, base address
PERI_MS_PPU_FX347_MS_SIZE	0x40025EE4	FULL	Master region, size
PERI_MS_PPU_FX347_MS_ATT0	0x40025EF0	FULL	Master attributes 0
PERI_MS_PPU_FX347_MS_ATT1	0x40025EF4	FULL	Master attributes 1
PERI_MS_PPU_FX347_MS_ATT2	0x40025EF8	FULL	Master attributes 2
PERI_MS_PPU_FX347_MS_ATT3	0x40025EFC	FULL	Master attributes 3

21.365 PPU_FX 348

Register Name	Address	Permission	Description
PERI_MS_PPU_FX348_SL_ADDR	0x40025F00	FULL	Slave region, base address
PERI_MS_PPU_FX348_SL_SIZE	0x40025F04	FULL	Slave region, size
PERI_MS_PPU_FX348_SL_ATT0	0x40025F10	FULL	Slave attributes 0
PERI_MS_PPU_FX348_SL_ATT1	0x40025F14	FULL	Slave attributes 1
PERI_MS_PPU_FX348_SL_ATT2	0x40025F18	FULL	Slave attributes 2
PERI_MS_PPU_FX348_SL_ATT3	0x40025F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX348_MS_ADDR	0x40025F20	FULL	Master region, base address
PERI_MS_PPU_FX348_MS_SIZE	0x40025F24	FULL	Master region, size
PERI_MS_PPU_FX348_MS_ATT0	0x40025F30	FULL	Master attributes 0
PERI_MS_PPU_FX348_MS_ATT1	0x40025F34	FULL	Master attributes 1
PERI_MS_PPU_FX348_MS_ATT2	0x40025F38	FULL	Master attributes 2
PERI_MS_PPU_FX348_MS_ATT3	0x40025F3C	FULL	Master attributes 3

21.366 PPU_FX 349

Register Name	Address	Permission	Description
PERI_MS_PPU_FX349_SL_ADDR	0x40025F40	FULL	Slave region, base address
PERI_MS_PPU_FX349_SL_SIZE	0x40025F44	FULL	Slave region, size
PERI_MS_PPU_FX349_SL_ATT0	0x40025F50	FULL	Slave attributes 0
PERI_MS_PPU_FX349_SL_ATT1	0x40025F54	FULL	Slave attributes 1
PERI_MS_PPU_FX349_SL_ATT2	0x40025F58	FULL	Slave attributes 2
PERI_MS_PPU_FX349_SL_ATT3	0x40025F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX349_MS_ADDR	0x40025F60	FULL	Master region, base address
PERI_MS_PPU_FX349_MS_SIZE	0x40025F64	FULL	Master region, size
PERI_MS_PPU_FX349_MS_ATT0	0x40025F70	FULL	Master attributes 0
PERI_MS_PPU_FX349_MS_ATT1	0x40025F74	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX349_MS_ATT2	0x40025F78	FULL	Master attributes 2
PERI_MS_PPU_FX349_MS_ATT3	0x40025F7C	FULL	Master attributes 3

21.367 PPU_FX 350

Register Name	Address	Permission	Description
PERI_MS_PPU_FX350_SL_ADDR	0x40025F80	FULL	Slave region, base address
PERI_MS_PPU_FX350_SL_SIZE	0x40025F84	FULL	Slave region, size
PERI_MS_PPU_FX350_SL_ATT0	0x40025F90	FULL	Slave attributes 0
PERI_MS_PPU_FX350_SL_ATT1	0x40025F94	FULL	Slave attributes 1
PERI_MS_PPU_FX350_SL_ATT2	0x40025F98	FULL	Slave attributes 2
PERI_MS_PPU_FX350_SL_ATT3	0x40025F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX350_MS_ADDR	0x40025FA0	FULL	Master region, base address
PERI_MS_PPU_FX350_MS_SIZE	0x40025FA4	FULL	Master region, size
PERI_MS_PPU_FX350_MS_ATT0	0x40025FB0	FULL	Master attributes 0
PERI_MS_PPU_FX350_MS_ATT1	0x40025FB4	FULL	Master attributes 1
PERI_MS_PPU_FX350_MS_ATT2	0x40025FB8	FULL	Master attributes 2
PERI_MS_PPU_FX350_MS_ATT3	0x40025FBC	FULL	Master attributes 3

21.368 PPU_FX 351

Register Name	Address	Permission	Description
PERI_MS_PPU_FX351_SL_ADDR	0x40025FC0	FULL	Slave region, base address
PERI_MS_PPU_FX351_SL_SIZE	0x40025FC4	FULL	Slave region, size
PERI_MS_PPU_FX351_SL_ATT0	0x40025FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX351_SL_ATT1	0x40025FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX351_SL_ATT2	0x40025FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX351_SL_ATT3	0x40025FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX351_MS_ADDR	0x40025FE0	FULL	Master region, base address
PERI_MS_PPU_FX351_MS_SIZE	0x40025FE4	FULL	Master region, size
PERI_MS_PPU_FX351_MS_ATT0	0x40025FF0	FULL	Master attributes 0
PERI_MS_PPU_FX351_MS_ATT1	0x40025FF4	FULL	Master attributes 1
PERI_MS_PPU_FX351_MS_ATT2	0x40025FF8	FULL	Master attributes 2
PERI_MS_PPU_FX351_MS_ATT3	0x40025FFC	FULL	Master attributes 3

21.369 PPU_FX 352

Register Name	Address	Permission	Description
PERI_MS_PPU_FX352_SL_ADDR	0x40026000	FULL	Slave region, base address
PERI_MS_PPU_FX352_SL_SIZE	0x40026004	FULL	Slave region, size
PERI_MS_PPU_FX352_SL_ATT0	0x40026010	FULL	Slave attributes 0
PERI_MS_PPU_FX352_SL_ATT1	0x40026014	FULL	Slave attributes 1
PERI_MS_PPU_FX352_SL_ATT2	0x40026018	FULL	Slave attributes 2
PERI_MS_PPU_FX352_SL_ATT3	0x4002601C	FULL	Slave attributes 3
PERI_MS_PPU_FX352_MS_ADDR	0x40026020	FULL	Master region, base address
PERI_MS_PPU_FX352_MS_SIZE	0x40026024	FULL	Master region, size
PERI_MS_PPU_FX352_MS_ATT0	0x40026030	FULL	Master attributes 0
PERI_MS_PPU_FX352_MS_ATT1	0x40026034	FULL	Master attributes 1
PERI_MS_PPU_FX352_MS_ATT2	0x40026038	FULL	Master attributes 2
PERI_MS_PPU_FX352_MS_ATT3	0x4002603C	FULL	Master attributes 3

21.370 PPU_FX 353

Register Name	Address	Permission	Description
PERI_MS_PPU_FX353_SL_ADDR	0x40026040	FULL	Slave region, base address
PERI_MS_PPU_FX353_SL_SIZE	0x40026044	FULL	Slave region, size
PERI_MS_PPU_FX353_SL_ATT0	0x40026050	FULL	Slave attributes 0
PERI_MS_PPU_FX353_SL_ATT1	0x40026054	FULL	Slave attributes 1
PERI_MS_PPU_FX353_SL_ATT2	0x40026058	FULL	Slave attributes 2
PERI_MS_PPU_FX353_SL_ATT3	0x4002605C	FULL	Slave attributes 3
PERI_MS_PPU_FX353_MS_ADDR	0x40026060	FULL	Master region, base address
PERI_MS_PPU_FX353_MS_SIZE	0x40026064	FULL	Master region, size
PERI_MS_PPU_FX353_MS_ATT0	0x40026070	FULL	Master attributes 0
PERI_MS_PPU_FX353_MS_ATT1	0x40026074	FULL	Master attributes 1
PERI_MS_PPU_FX353_MS_ATT2	0x40026078	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX353_MS_ATT3	0x4002607C	FULL	Master attributes 3

21.371 PPU_FX 354

Register Name	Address	Permission	Description
PERI_MS_PPU_FX354_SL_ADDR	0x40026080	FULL	Slave region, base address
PERI_MS_PPU_FX354_SL_SIZE	0x40026084	FULL	Slave region, size
PERI_MS_PPU_FX354_SL_ATT0	0x40026090	FULL	Slave attributes 0
PERI_MS_PPU_FX354_SL_ATT1	0x40026094	FULL	Slave attributes 1
PERI_MS_PPU_FX354_SL_ATT2	0x40026098	FULL	Slave attributes 2
PERI_MS_PPU_FX354_SL_ATT3	0x4002609C	FULL	Slave attributes 3
PERI_MS_PPU_FX354_MS_ADDR	0x400260A0	FULL	Master region, base address
PERI_MS_PPU_FX354_MS_SIZE	0x400260A4	FULL	Master region, size
PERI_MS_PPU_FX354_MS_ATT0	0x400260B0	FULL	Master attributes 0
PERI_MS_PPU_FX354_MS_ATT1	0x400260B4	FULL	Master attributes 1
PERI_MS_PPU_FX354_MS_ATT2	0x400260B8	FULL	Master attributes 2
PERI_MS_PPU_FX354_MS_ATT3	0x400260BC	FULL	Master attributes 3

21.372 PPU_FX 355

Register Name	Address	Permission	Description
PERI_MS_PPU_FX355_SL_ADDR	0x400260C0	FULL	Slave region, base address
PERI_MS_PPU_FX355_SL_SIZE	0x400260C4	FULL	Slave region, size
PERI_MS_PPU_FX355_SL_ATT0	0x400260D0	FULL	Slave attributes 0
PERI_MS_PPU_FX355_SL_ATT1	0x400260D4	FULL	Slave attributes 1
PERI_MS_PPU_FX355_SL_ATT2	0x400260D8	FULL	Slave attributes 2
PERI_MS_PPU_FX355_SL_ATT3	0x400260DC	FULL	Slave attributes 3
PERI_MS_PPU_FX355_MS_ADDR	0x400260E0	FULL	Master region, base address
PERI_MS_PPU_FX355_MS_SIZE	0x400260E4	FULL	Master region, size
PERI_MS_PPU_FX355_MS_ATT0	0x400260F0	FULL	Master attributes 0
PERI_MS_PPU_FX355_MS_ATT1	0x400260F4	FULL	Master attributes 1
PERI_MS_PPU_FX355_MS_ATT2	0x400260F8	FULL	Master attributes 2
PERI_MS_PPU_FX355_MS_ATT3	0x400260FC	FULL	Master attributes 3

21.373 PPU_FX 356

Register Name	Address	Permission	Description
PERI_MS_PPU_FX356_SL_ADDR	0x40026100	FULL	Slave region, base address
PERI_MS_PPU_FX356_SL_SIZE	0x40026104	FULL	Slave region, size
PERI_MS_PPU_FX356_SL_ATT0	0x40026110	FULL	Slave attributes 0
PERI_MS_PPU_FX356_SL_ATT1	0x40026114	FULL	Slave attributes 1
PERI_MS_PPU_FX356_SL_ATT2	0x40026118	FULL	Slave attributes 2
PERI_MS_PPU_FX356_SL_ATT3	0x4002611C	FULL	Slave attributes 3
PERI_MS_PPU_FX356_MS_ADDR	0x40026120	FULL	Master region, base address
PERI_MS_PPU_FX356_MS_SIZE	0x40026124	FULL	Master region, size
PERI_MS_PPU_FX356_MS_ATT0	0x40026130	FULL	Master attributes 0
PERI_MS_PPU_FX356_MS_ATT1	0x40026134	FULL	Master attributes 1
PERI_MS_PPU_FX356_MS_ATT2	0x40026138	FULL	Master attributes 2
PERI_MS_PPU_FX356_MS_ATT3	0x4002613C	FULL	Master attributes 3

21.374 PPU_FX 357

Register Name	Address	Permission	Description
PERI_MS_PPU_FX357_SL_ADDR	0x40026140	FULL	Slave region, base address
PERI_MS_PPU_FX357_SL_SIZE	0x40026144	FULL	Slave region, size
PERI_MS_PPU_FX357_SL_ATT0	0x40026150	FULL	Slave attributes 0
PERI_MS_PPU_FX357_SL_ATT1	0x40026154	FULL	Slave attributes 1
PERI_MS_PPU_FX357_SL_ATT2	0x40026158	FULL	Slave attributes 2
PERI_MS_PPU_FX357_SL_ATT3	0x4002615C	FULL	Slave attributes 3
PERI_MS_PPU_FX357_MS_ADDR	0x40026160	FULL	Master region, base address
PERI_MS_PPU_FX357_MS_SIZE	0x40026164	FULL	Master region, size
PERI_MS_PPU_FX357_MS_ATT0	0x40026170	FULL	Master attributes 0
PERI_MS_PPU_FX357_MS_ATT1	0x40026174	FULL	Master attributes 1
PERI_MS_PPU_FX357_MS_ATT2	0x40026178	FULL	Master attributes 2
PERI_MS_PPU_FX357_MS_ATT3	0x4002617C	FULL	Master attributes 3

21.375 PPU_FX 358

Register Name	Address	Permission	Description
PERI_MS_PPU_FX358_SL_ADDR	0x40026180	FULL	Slave region, base address
PERI_MS_PPU_FX358_SL_SIZE	0x40026184	FULL	Slave region, size
PERI_MS_PPU_FX358_SL_ATT0	0x40026190	FULL	Slave attributes 0
PERI_MS_PPU_FX358_SL_ATT1	0x40026194	FULL	Slave attributes 1
PERI_MS_PPU_FX358_SL_ATT2	0x40026198	FULL	Slave attributes 2
PERI_MS_PPU_FX358_SL_ATT3	0x4002619C	FULL	Slave attributes 3
PERI_MS_PPU_FX358_MS_ADDR	0x400261A0	FULL	Master region, base address
PERI_MS_PPU_FX358_MS_SIZE	0x400261A4	FULL	Master region, size
PERI_MS_PPU_FX358_MS_ATT0	0x400261B0	FULL	Master attributes 0
PERI_MS_PPU_FX358_MS_ATT1	0x400261B4	FULL	Master attributes 1
PERI_MS_PPU_FX358_MS_ATT2	0x400261B8	FULL	Master attributes 2
PERI_MS_PPU_FX358_MS_ATT3	0x400261BC	FULL	Master attributes 3

21.376 PPU_FX 359

Register Name	Address	Permission	Description
PERI_MS_PPU_FX359_SL_ADDR	0x400261C0	FULL	Slave region, base address
PERI_MS_PPU_FX359_SL_SIZE	0x400261C4	FULL	Slave region, size
PERI_MS_PPU_FX359_SL_ATT0	0x400261D0	FULL	Slave attributes 0
PERI_MS_PPU_FX359_SL_ATT1	0x400261D4	FULL	Slave attributes 1
PERI_MS_PPU_FX359_SL_ATT2	0x400261D8	FULL	Slave attributes 2
PERI_MS_PPU_FX359_SL_ATT3	0x400261DC	FULL	Slave attributes 3
PERI_MS_PPU_FX359_MS_ADDR	0x400261E0	FULL	Master region, base address
PERI_MS_PPU_FX359_MS_SIZE	0x400261E4	FULL	Master region, size
PERI_MS_PPU_FX359_MS_ATT0	0x400261F0	FULL	Master attributes 0
PERI_MS_PPU_FX359_MS_ATT1	0x400261F4	FULL	Master attributes 1
PERI_MS_PPU_FX359_MS_ATT2	0x400261F8	FULL	Master attributes 2
PERI_MS_PPU_FX359_MS_ATT3	0x400261FC	FULL	Master attributes 3

21.377 PPU_FX 360

Register Name	Address	Permission	Description
PERI_MS_PPU_FX360_SL_ADDR	0x40026200	FULL	Slave region, base address
PERI_MS_PPU_FX360_SL_SIZE	0x40026204	FULL	Slave region, size
PERI_MS_PPU_FX360_SL_ATT0	0x40026210	FULL	Slave attributes 0
PERI_MS_PPU_FX360_SL_ATT1	0x40026214	FULL	Slave attributes 1
PERI_MS_PPU_FX360_SL_ATT2	0x40026218	FULL	Slave attributes 2
PERI_MS_PPU_FX360_SL_ATT3	0x4002621C	FULL	Slave attributes 3
PERI_MS_PPU_FX360_MS_ADDR	0x40026220	FULL	Master region, base address
PERI_MS_PPU_FX360_MS_SIZE	0x40026224	FULL	Master region, size
PERI_MS_PPU_FX360_MS_ATT0	0x40026230	FULL	Master attributes 0
PERI_MS_PPU_FX360_MS_ATT1	0x40026234	FULL	Master attributes 1
PERI_MS_PPU_FX360_MS_ATT2	0x40026238	FULL	Master attributes 2
PERI_MS_PPU_FX360_MS_ATT3	0x4002623C	FULL	Master attributes 3

21.378 PPU_FX 361

Register Name	Address	Permission	Description
PERI_MS_PPU_FX361_SL_ADDR	0x40026240	FULL	Slave region, base address
PERI_MS_PPU_FX361_SL_SIZE	0x40026244	FULL	Slave region, size
PERI_MS_PPU_FX361_SL_ATT0	0x40026250	FULL	Slave attributes 0
PERI_MS_PPU_FX361_SL_ATT1	0x40026254	FULL	Slave attributes 1
PERI_MS_PPU_FX361_SL_ATT2	0x40026258	FULL	Slave attributes 2
PERI_MS_PPU_FX361_SL_ATT3	0x4002625C	FULL	Slave attributes 3
PERI_MS_PPU_FX361_MS_ADDR	0x40026260	FULL	Master region, base address
PERI_MS_PPU_FX361_MS_SIZE	0x40026264	FULL	Master region, size
PERI_MS_PPU_FX361_MS_ATT0	0x40026270	FULL	Master attributes 0
PERI_MS_PPU_FX361_MS_ATT1	0x40026274	FULL	Master attributes 1
PERI_MS_PPU_FX361_MS_ATT2	0x40026278	FULL	Master attributes 2
PERI_MS_PPU_FX361_MS_ATT3	0x4002627C	FULL	Master attributes 3

21.379 PPU_FX 362

Register Name	Address	Permission	Description
PERI_MS_PPU_FX362_SL_ADDR	0x40026280	FULL	Slave region, base address
PERI_MS_PPU_FX362_SL_SIZE	0x40026284	FULL	Slave region, size
PERI_MS_PPU_FX362_SL_ATT0	0x40026290	FULL	Slave attributes 0
PERI_MS_PPU_FX362_SL_ATT1	0x40026294	FULL	Slave attributes 1
PERI_MS_PPU_FX362_SL_ATT2	0x40026298	FULL	Slave attributes 2
PERI_MS_PPU_FX362_SL_ATT3	0x4002629C	FULL	Slave attributes 3
PERI_MS_PPU_FX362_MS_ADDR	0x400262A0	FULL	Master region, base address
PERI_MS_PPU_FX362_MS_SIZE	0x400262A4	FULL	Master region, size
PERI_MS_PPU_FX362_MS_ATT0	0x400262B0	FULL	Master attributes 0
PERI_MS_PPU_FX362_MS_ATT1	0x400262B4	FULL	Master attributes 1
PERI_MS_PPU_FX362_MS_ATT2	0x400262B8	FULL	Master attributes 2
PERI_MS_PPU_FX362_MS_ATT3	0x400262BC	FULL	Master attributes 3

21.380 PPU_FX 363

Register Name	Address	Permission	Description
PERI_MS_PPU_FX363_SL_ADDR	0x400262C0	FULL	Slave region, base address
PERI_MS_PPU_FX363_SL_SIZE	0x400262C4	FULL	Slave region, size
PERI_MS_PPU_FX363_SL_ATT0	0x400262D0	FULL	Slave attributes 0
PERI_MS_PPU_FX363_SL_ATT1	0x400262D4	FULL	Slave attributes 1
PERI_MS_PPU_FX363_SL_ATT2	0x400262D8	FULL	Slave attributes 2
PERI_MS_PPU_FX363_SL_ATT3	0x400262DC	FULL	Slave attributes 3
PERI_MS_PPU_FX363_MS_ADDR	0x400262E0	FULL	Master region, base address
PERI_MS_PPU_FX363_MS_SIZE	0x400262E4	FULL	Master region, size
PERI_MS_PPU_FX363_MS_ATT0	0x400262F0	FULL	Master attributes 0
PERI_MS_PPU_FX363_MS_ATT1	0x400262F4	FULL	Master attributes 1
PERI_MS_PPU_FX363_MS_ATT2	0x400262F8	FULL	Master attributes 2
PERI_MS_PPU_FX363_MS_ATT3	0x400262FC	FULL	Master attributes 3

21.381 PPU_FX 364

Register Name	Address	Permission	Description
PERI_MS_PPU_FX364_SL_ADDR	0x40026300	FULL	Slave region, base address
PERI_MS_PPU_FX364_SL_SIZE	0x40026304	FULL	Slave region, size
PERI_MS_PPU_FX364_SL_ATT0	0x40026310	FULL	Slave attributes 0
PERI_MS_PPU_FX364_SL_ATT1	0x40026314	FULL	Slave attributes 1
PERI_MS_PPU_FX364_SL_ATT2	0x40026318	FULL	Slave attributes 2
PERI_MS_PPU_FX364_SL_ATT3	0x4002631C	FULL	Slave attributes 3
PERI_MS_PPU_FX364_MS_ADDR	0x40026320	FULL	Master region, base address
PERI_MS_PPU_FX364_MS_SIZE	0x40026324	FULL	Master region, size
PERI_MS_PPU_FX364_MS_ATT0	0x40026330	FULL	Master attributes 0
PERI_MS_PPU_FX364_MS_ATT1	0x40026334	FULL	Master attributes 1
PERI_MS_PPU_FX364_MS_ATT2	0x40026338	FULL	Master attributes 2
PERI_MS_PPU_FX364_MS_ATT3	0x4002633C	FULL	Master attributes 3

21.382 PPU_FX 365

Register Name	Address	Permission	Description
PERI_MS_PPU_FX365_SL_ADDR	0x40026340	FULL	Slave region, base address
PERI_MS_PPU_FX365_SL_SIZE	0x40026344	FULL	Slave region, size
PERI_MS_PPU_FX365_SL_ATT0	0x40026350	FULL	Slave attributes 0
PERI_MS_PPU_FX365_SL_ATT1	0x40026354	FULL	Slave attributes 1
PERI_MS_PPU_FX365_SL_ATT2	0x40026358	FULL	Slave attributes 2
PERI_MS_PPU_FX365_SL_ATT3	0x4002635C	FULL	Slave attributes 3
PERI_MS_PPU_FX365_MS_ADDR	0x40026360	FULL	Master region, base address
PERI_MS_PPU_FX365_MS_SIZE	0x40026364	FULL	Master region, size
PERI_MS_PPU_FX365_MS_ATT0	0x40026370	FULL	Master attributes 0
PERI_MS_PPU_FX365_MS_ATT1	0x40026374	FULL	Master attributes 1
PERI_MS_PPU_FX365_MS_ATT2	0x40026378	FULL	Master attributes 2
PERI_MS_PPU_FX365_MS_ATT3	0x4002637C	FULL	Master attributes 3

21.383 PPU_FX 366

Register Name	Address	Permission	Description
PERI_MS_PPU_FX366_SL_ADDR	0x40026380	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX366_SL_SIZE	0x40026384	FULL	Slave region, size
PERI_MS_PPU_FX366_SL_ATT0	0x40026390	FULL	Slave attributes 0
PERI_MS_PPU_FX366_SL_ATT1	0x40026394	FULL	Slave attributes 1
PERI_MS_PPU_FX366_SL_ATT2	0x40026398	FULL	Slave attributes 2
PERI_MS_PPU_FX366_SL_ATT3	0x4002639C	FULL	Slave attributes 3
PERI_MS_PPU_FX366_MS_ADDR	0x400263A0	FULL	Master region, base address
PERI_MS_PPU_FX366_MS_SIZE	0x400263A4	FULL	Master region, size
PERI_MS_PPU_FX366_MS_ATT0	0x400263B0	FULL	Master attributes 0
PERI_MS_PPU_FX366_MS_ATT1	0x400263B4	FULL	Master attributes 1
PERI_MS_PPU_FX366_MS_ATT2	0x400263B8	FULL	Master attributes 2
PERI_MS_PPU_FX366_MS_ATT3	0x400263BC	FULL	Master attributes 3

21.384 PPU_FX 367

Register Name	Address	Permission	Description
PERI_MS_PPU_FX367_SL_ADDR	0x400263C0	FULL	Slave region, base address
PERI_MS_PPU_FX367_SL_SIZE	0x400263C4	FULL	Slave region, size
PERI_MS_PPU_FX367_SL_ATT0	0x400263D0	FULL	Slave attributes 0
PERI_MS_PPU_FX367_SL_ATT1	0x400263D4	FULL	Slave attributes 1
PERI_MS_PPU_FX367_SL_ATT2	0x400263D8	FULL	Slave attributes 2
PERI_MS_PPU_FX367_SL_ATT3	0x400263DC	FULL	Slave attributes 3
PERI_MS_PPU_FX367_MS_ADDR	0x400263E0	FULL	Master region, base address
PERI_MS_PPU_FX367_MS_SIZE	0x400263E4	FULL	Master region, size
PERI_MS_PPU_FX367_MS_ATT0	0x400263F0	FULL	Master attributes 0
PERI_MS_PPU_FX367_MS_ATT1	0x400263F4	FULL	Master attributes 1
PERI_MS_PPU_FX367_MS_ATT2	0x400263F8	FULL	Master attributes 2
PERI_MS_PPU_FX367_MS_ATT3	0x400263FC	FULL	Master attributes 3

21.385 PPU_FX 368

Register Name	Address	Permission	Description
PERI_MS_PPU_FX368_SL_ADDR	0x40026400	FULL	Slave region, base address
PERI_MS_PPU_FX368_SL_SIZE	0x40026404	FULL	Slave region, size
PERI_MS_PPU_FX368_SL_ATT0	0x40026410	FULL	Slave attributes 0
PERI_MS_PPU_FX368_SL_ATT1	0x40026414	FULL	Slave attributes 1
PERI_MS_PPU_FX368_SL_ATT2	0x40026418	FULL	Slave attributes 2
PERI_MS_PPU_FX368_SL_ATT3	0x4002641C	FULL	Slave attributes 3
PERI_MS_PPU_FX368_MS_ADDR	0x40026420	FULL	Master region, base address
PERI_MS_PPU_FX368_MS_SIZE	0x40026424	FULL	Master region, size
PERI_MS_PPU_FX368_MS_ATT0	0x40026430	FULL	Master attributes 0
PERI_MS_PPU_FX368_MS_ATT1	0x40026434	FULL	Master attributes 1
PERI_MS_PPU_FX368_MS_ATT2	0x40026438	FULL	Master attributes 2
PERI_MS_PPU_FX368_MS_ATT3	0x4002643C	FULL	Master attributes 3

21.386 PPU_FX 369

Register Name	Address	Permission	Description
PERI_MS_PPU_FX369_SL_ADDR	0x40026440	FULL	Slave region, base address
PERI_MS_PPU_FX369_SL_SIZE	0x40026444	FULL	Slave region, size
PERI_MS_PPU_FX369_SL_ATT0	0x40026450	FULL	Slave attributes 0
PERI_MS_PPU_FX369_SL_ATT1	0x40026454	FULL	Slave attributes 1
PERI_MS_PPU_FX369_SL_ATT2	0x40026458	FULL	Slave attributes 2
PERI_MS_PPU_FX369_SL_ATT3	0x4002645C	FULL	Slave attributes 3
PERI_MS_PPU_FX369_MS_ADDR	0x40026460	FULL	Master region, base address
PERI_MS_PPU_FX369_MS_SIZE	0x40026464	FULL	Master region, size
PERI_MS_PPU_FX369_MS_ATT0	0x40026470	FULL	Master attributes 0
PERI_MS_PPU_FX369_MS_ATT1	0x40026474	FULL	Master attributes 1
PERI_MS_PPU_FX369_MS_ATT2	0x40026478	FULL	Master attributes 2
PERI_MS_PPU_FX369_MS_ATT3	0x4002647C	FULL	Master attributes 3

21.387 PPU_FX 370

Register Name	Address	Permission	Description
PERI_MS_PPU_FX370_SL_ADDR	0x40026480	FULL	Slave region, base address
PERI_MS_PPU_FX370_SL_SIZE	0x40026484	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX370_SL_ATT0	0x40026490	FULL	Slave attributes 0
PERI_MS_PPU_FX370_SL_ATT1	0x40026494	FULL	Slave attributes 1
PERI_MS_PPU_FX370_SL_ATT2	0x40026498	FULL	Slave attributes 2
PERI_MS_PPU_FX370_SL_ATT3	0x4002649C	FULL	Slave attributes 3
PERI_MS_PPU_FX370_MS_ADDR	0x400264A0	FULL	Master region, base address
PERI_MS_PPU_FX370_MS_SIZE	0x400264A4	FULL	Master region, size
PERI_MS_PPU_FX370_MS_ATT0	0x400264B0	FULL	Master attributes 0
PERI_MS_PPU_FX370_MS_ATT1	0x400264B4	FULL	Master attributes 1
PERI_MS_PPU_FX370_MS_ATT2	0x400264B8	FULL	Master attributes 2
PERI_MS_PPU_FX370_MS_ATT3	0x400264BC	FULL	Master attributes 3

21.388 PPU_FX 371

Register Name	Address	Permission	Description
PERI_MS_PPU_FX371_SL_ADDR	0x400264C0	FULL	Slave region, base address
PERI_MS_PPU_FX371_SL_SIZE	0x400264C4	FULL	Slave region, size
PERI_MS_PPU_FX371_SL_ATT0	0x400264D0	FULL	Slave attributes 0
PERI_MS_PPU_FX371_SL_ATT1	0x400264D4	FULL	Slave attributes 1
PERI_MS_PPU_FX371_SL_ATT2	0x400264D8	FULL	Slave attributes 2
PERI_MS_PPU_FX371_SL_ATT3	0x400264DC	FULL	Slave attributes 3
PERI_MS_PPU_FX371_MS_ADDR	0x400264E0	FULL	Master region, base address
PERI_MS_PPU_FX371_MS_SIZE	0x400264E4	FULL	Master region, size
PERI_MS_PPU_FX371_MS_ATT0	0x400264F0	FULL	Master attributes 0
PERI_MS_PPU_FX371_MS_ATT1	0x400264F4	FULL	Master attributes 1
PERI_MS_PPU_FX371_MS_ATT2	0x400264F8	FULL	Master attributes 2
PERI_MS_PPU_FX371_MS_ATT3	0x400264FC	FULL	Master attributes 3

21.389 PPU_FX 372

Register Name	Address	Permission	Description
PERI_MS_PPU_FX372_SL_ADDR	0x40026500	FULL	Slave region, base address
PERI_MS_PPU_FX372_SL_SIZE	0x40026504	FULL	Slave region, size
PERI_MS_PPU_FX372_SL_ATT0	0x40026510	FULL	Slave attributes 0
PERI_MS_PPU_FX372_SL_ATT1	0x40026514	FULL	Slave attributes 1
PERI_MS_PPU_FX372_SL_ATT2	0x40026518	FULL	Slave attributes 2
PERI_MS_PPU_FX372_SL_ATT3	0x4002651C	FULL	Slave attributes 3
PERI_MS_PPU_FX372_MS_ADDR	0x40026520	FULL	Master region, base address
PERI_MS_PPU_FX372_MS_SIZE	0x40026524	FULL	Master region, size
PERI_MS_PPU_FX372_MS_ATT0	0x40026530	FULL	Master attributes 0
PERI_MS_PPU_FX372_MS_ATT1	0x40026534	FULL	Master attributes 1
PERI_MS_PPU_FX372_MS_ATT2	0x40026538	FULL	Master attributes 2
PERI_MS_PPU_FX372_MS_ATT3	0x4002653C	FULL	Master attributes 3

21.390 PPU_FX 373

Register Name	Address	Permission	Description
PERI_MS_PPU_FX373_SL_ADDR	0x40026540	FULL	Slave region, base address
PERI_MS_PPU_FX373_SL_SIZE	0x40026544	FULL	Slave region, size
PERI_MS_PPU_FX373_SL_ATT0	0x40026550	FULL	Slave attributes 0
PERI_MS_PPU_FX373_SL_ATT1	0x40026554	FULL	Slave attributes 1
PERI_MS_PPU_FX373_SL_ATT2	0x40026558	FULL	Slave attributes 2
PERI_MS_PPU_FX373_SL_ATT3	0x4002655C	FULL	Slave attributes 3
PERI_MS_PPU_FX373_MS_ADDR	0x40026560	FULL	Master region, base address
PERI_MS_PPU_FX373_MS_SIZE	0x40026564	FULL	Master region, size
PERI_MS_PPU_FX373_MS_ATT0	0x40026570	FULL	Master attributes 0
PERI_MS_PPU_FX373_MS_ATT1	0x40026574	FULL	Master attributes 1
PERI_MS_PPU_FX373_MS_ATT2	0x40026578	FULL	Master attributes 2
PERI_MS_PPU_FX373_MS_ATT3	0x4002657C	FULL	Master attributes 3

21.391 PPU_FX 374

Register Name	Address	Permission	Description
PERI_MS_PPU_FX374_SL_ADDR	0x40026580	FULL	Slave region, base address
PERI_MS_PPU_FX374_SL_SIZE	0x40026584	FULL	Slave region, size
PERI_MS_PPU_FX374_SL_ATT0	0x40026590	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX374_SL_ATT1	0x40026594	FULL	Slave attributes 1
PERI_MS_PPU_FX374_SL_ATT2	0x40026598	FULL	Slave attributes 2
PERI_MS_PPU_FX374_SL_ATT3	0x4002659C	FULL	Slave attributes 3
PERI_MS_PPU_FX374_MS_ADDR	0x400265A0	FULL	Master region, base address
PERI_MS_PPU_FX374_MS_SIZE	0x400265A4	FULL	Master region, size
PERI_MS_PPU_FX374_MS_ATT0	0x400265B0	FULL	Master attributes 0
PERI_MS_PPU_FX374_MS_ATT1	0x400265B4	FULL	Master attributes 1
PERI_MS_PPU_FX374_MS_ATT2	0x400265B8	FULL	Master attributes 2
PERI_MS_PPU_FX374_MS_ATT3	0x400265BC	FULL	Master attributes 3

21.392 PPU_FX 375

Register Name	Address	Permission	Description
PERI_MS_PPU_FX375_SL_ADDR	0x400265C0	FULL	Slave region, base address
PERI_MS_PPU_FX375_SL_SIZE	0x400265C4	FULL	Slave region, size
PERI_MS_PPU_FX375_SL_ATT0	0x400265D0	FULL	Slave attributes 0
PERI_MS_PPU_FX375_SL_ATT1	0x400265D4	FULL	Slave attributes 1
PERI_MS_PPU_FX375_SL_ATT2	0x400265D8	FULL	Slave attributes 2
PERI_MS_PPU_FX375_SL_ATT3	0x400265DC	FULL	Slave attributes 3
PERI_MS_PPU_FX375_MS_ADDR	0x400265E0	FULL	Master region, base address
PERI_MS_PPU_FX375_MS_SIZE	0x400265E4	FULL	Master region, size
PERI_MS_PPU_FX375_MS_ATT0	0x400265F0	FULL	Master attributes 0
PERI_MS_PPU_FX375_MS_ATT1	0x400265F4	FULL	Master attributes 1
PERI_MS_PPU_FX375_MS_ATT2	0x400265F8	FULL	Master attributes 2
PERI_MS_PPU_FX375_MS_ATT3	0x400265FC	FULL	Master attributes 3

21.393 PPU_FX 376

Register Name	Address	Permission	Description
PERI_MS_PPU_FX376_SL_ADDR	0x40026600	FULL	Slave region, base address
PERI_MS_PPU_FX376_SL_SIZE	0x40026604	FULL	Slave region, size
PERI_MS_PPU_FX376_SL_ATT0	0x40026610	FULL	Slave attributes 0
PERI_MS_PPU_FX376_SL_ATT1	0x40026614	FULL	Slave attributes 1
PERI_MS_PPU_FX376_SL_ATT2	0x40026618	FULL	Slave attributes 2
PERI_MS_PPU_FX376_SL_ATT3	0x4002661C	FULL	Slave attributes 3
PERI_MS_PPU_FX376_MS_ADDR	0x40026620	FULL	Master region, base address
PERI_MS_PPU_FX376_MS_SIZE	0x40026624	FULL	Master region, size
PERI_MS_PPU_FX376_MS_ATT0	0x40026630	FULL	Master attributes 0
PERI_MS_PPU_FX376_MS_ATT1	0x40026634	FULL	Master attributes 1
PERI_MS_PPU_FX376_MS_ATT2	0x40026638	FULL	Master attributes 2
PERI_MS_PPU_FX376_MS_ATT3	0x4002663C	FULL	Master attributes 3

21.394 PPU_FX 377

Register Name	Address	Permission	Description
PERI_MS_PPU_FX377_SL_ADDR	0x40026640	FULL	Slave region, base address
PERI_MS_PPU_FX377_SL_SIZE	0x40026644	FULL	Slave region, size
PERI_MS_PPU_FX377_SL_ATT0	0x40026650	FULL	Slave attributes 0
PERI_MS_PPU_FX377_SL_ATT1	0x40026654	FULL	Slave attributes 1
PERI_MS_PPU_FX377_SL_ATT2	0x40026658	FULL	Slave attributes 2
PERI_MS_PPU_FX377_SL_ATT3	0x4002665C	FULL	Slave attributes 3
PERI_MS_PPU_FX377_MS_ADDR	0x40026660	FULL	Master region, base address
PERI_MS_PPU_FX377_MS_SIZE	0x40026664	FULL	Master region, size
PERI_MS_PPU_FX377_MS_ATT0	0x40026670	FULL	Master attributes 0
PERI_MS_PPU_FX377_MS_ATT1	0x40026674	FULL	Master attributes 1
PERI_MS_PPU_FX377_MS_ATT2	0x40026678	FULL	Master attributes 2
PERI_MS_PPU_FX377_MS_ATT3	0x4002667C	FULL	Master attributes 3

21.395 PPU_FX 378

Register Name	Address	Permission	Description
PERI_MS_PPU_FX378_SL_ADDR	0x40026680	FULL	Slave region, base address
PERI_MS_PPU_FX378_SL_SIZE	0x40026684	FULL	Slave region, size
PERI_MS_PPU_FX378_SL_ATT0	0x40026690	FULL	Slave attributes 0
PERI_MS_PPU_FX378_SL_ATT1	0x40026694	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX378_SL_ATT2	0x40026698	FULL	Slave attributes 2
PERI_MS_PPU_FX378_SL_ATT3	0x4002669C	FULL	Slave attributes 3
PERI_MS_PPU_FX378_MS_ADDR	0x400266A0	FULL	Master region, base address
PERI_MS_PPU_FX378_MS_SIZE	0x400266A4	FULL	Master region, size
PERI_MS_PPU_FX378_MS_ATT0	0x400266B0	FULL	Master attributes 0
PERI_MS_PPU_FX378_MS_ATT1	0x400266B4	FULL	Master attributes 1
PERI_MS_PPU_FX378_MS_ATT2	0x400266B8	FULL	Master attributes 2
PERI_MS_PPU_FX378_MS_ATT3	0x400266BC	FULL	Master attributes 3

21.396 PPU_FX 379

Register Name	Address	Permission	Description
PERI_MS_PPU_FX379_SL_ADDR	0x400266C0	FULL	Slave region, base address
PERI_MS_PPU_FX379_SL_SIZE	0x400266C4	FULL	Slave region, size
PERI_MS_PPU_FX379_SL_ATT0	0x400266D0	FULL	Slave attributes 0
PERI_MS_PPU_FX379_SL_ATT1	0x400266D4	FULL	Slave attributes 1
PERI_MS_PPU_FX379_SL_ATT2	0x400266D8	FULL	Slave attributes 2
PERI_MS_PPU_FX379_SL_ATT3	0x400266DC	FULL	Slave attributes 3
PERI_MS_PPU_FX379_MS_ADDR	0x400266E0	FULL	Master region, base address
PERI_MS_PPU_FX379_MS_SIZE	0x400266E4	FULL	Master region, size
PERI_MS_PPU_FX379_MS_ATT0	0x400266F0	FULL	Master attributes 0
PERI_MS_PPU_FX379_MS_ATT1	0x400266F4	FULL	Master attributes 1
PERI_MS_PPU_FX379_MS_ATT2	0x400266F8	FULL	Master attributes 2
PERI_MS_PPU_FX379_MS_ATT3	0x400266FC	FULL	Master attributes 3

21.397 PPU_FX 380

Register Name	Address	Permission	Description
PERI_MS_PPU_FX380_SL_ADDR	0x40026700	FULL	Slave region, base address
PERI_MS_PPU_FX380_SL_SIZE	0x40026704	FULL	Slave region, size
PERI_MS_PPU_FX380_SL_ATT0	0x40026710	FULL	Slave attributes 0
PERI_MS_PPU_FX380_SL_ATT1	0x40026714	FULL	Slave attributes 1
PERI_MS_PPU_FX380_SL_ATT2	0x40026718	FULL	Slave attributes 2
PERI_MS_PPU_FX380_SL_ATT3	0x4002671C	FULL	Slave attributes 3
PERI_MS_PPU_FX380_MS_ADDR	0x40026720	FULL	Master region, base address
PERI_MS_PPU_FX380_MS_SIZE	0x40026724	FULL	Master region, size
PERI_MS_PPU_FX380_MS_ATT0	0x40026730	FULL	Master attributes 0
PERI_MS_PPU_FX380_MS_ATT1	0x40026734	FULL	Master attributes 1
PERI_MS_PPU_FX380_MS_ATT2	0x40026738	FULL	Master attributes 2
PERI_MS_PPU_FX380_MS_ATT3	0x4002673C	FULL	Master attributes 3

21.398 PPU_FX 381

Register Name	Address	Permission	Description
PERI_MS_PPU_FX381_SL_ADDR	0x40026740	FULL	Slave region, base address
PERI_MS_PPU_FX381_SL_SIZE	0x40026744	FULL	Slave region, size
PERI_MS_PPU_FX381_SL_ATT0	0x40026750	FULL	Slave attributes 0
PERI_MS_PPU_FX381_SL_ATT1	0x40026754	FULL	Slave attributes 1
PERI_MS_PPU_FX381_SL_ATT2	0x40026758	FULL	Slave attributes 2
PERI_MS_PPU_FX381_SL_ATT3	0x4002675C	FULL	Slave attributes 3
PERI_MS_PPU_FX381_MS_ADDR	0x40026760	FULL	Master region, base address
PERI_MS_PPU_FX381_MS_SIZE	0x40026764	FULL	Master region, size
PERI_MS_PPU_FX381_MS_ATT0	0x40026770	FULL	Master attributes 0
PERI_MS_PPU_FX381_MS_ATT1	0x40026774	FULL	Master attributes 1
PERI_MS_PPU_FX381_MS_ATT2	0x40026778	FULL	Master attributes 2
PERI_MS_PPU_FX381_MS_ATT3	0x4002677C	FULL	Master attributes 3

21.399 PPU_FX 382

Register Name	Address	Permission	Description
PERI_MS_PPU_FX382_SL_ADDR	0x40026780	FULL	Slave region, base address
PERI_MS_PPU_FX382_SL_SIZE	0x40026784	FULL	Slave region, size
PERI_MS_PPU_FX382_SL_ATT0	0x40026790	FULL	Slave attributes 0
PERI_MS_PPU_FX382_SL_ATT1	0x40026794	FULL	Slave attributes 1
PERI_MS_PPU_FX382_SL_ATT2	0x40026798	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX382_SL_ATT3	0x4002679C	FULL	Slave attributes 3
PERI_MS_PPU_FX382_MS_ADDR	0x400267A0	FULL	Master region, base address
PERI_MS_PPU_FX382_MS_SIZE	0x400267A4	FULL	Master region, size
PERI_MS_PPU_FX382_MS_ATT0	0x400267B0	FULL	Master attributes 0
PERI_MS_PPU_FX382_MS_ATT1	0x400267B4	FULL	Master attributes 1
PERI_MS_PPU_FX382_MS_ATT2	0x400267B8	FULL	Master attributes 2
PERI_MS_PPU_FX382_MS_ATT3	0x400267BC	FULL	Master attributes 3

21.400 PPU_FX 383

Register Name	Address	Permission	Description
PERI_MS_PPU_FX383_SL_ADDR	0x400267C0	FULL	Slave region, base address
PERI_MS_PPU_FX383_SL_SIZE	0x400267C4	FULL	Slave region, size
PERI_MS_PPU_FX383_SL_ATT0	0x400267D0	FULL	Slave attributes 0
PERI_MS_PPU_FX383_SL_ATT1	0x400267D4	FULL	Slave attributes 1
PERI_MS_PPU_FX383_SL_ATT2	0x400267D8	FULL	Slave attributes 2
PERI_MS_PPU_FX383_SL_ATT3	0x400267DC	FULL	Slave attributes 3
PERI_MS_PPU_FX383_MS_ADDR	0x400267E0	FULL	Master region, base address
PERI_MS_PPU_FX383_MS_SIZE	0x400267E4	FULL	Master region, size
PERI_MS_PPU_FX383_MS_ATT0	0x400267F0	FULL	Master attributes 0
PERI_MS_PPU_FX383_MS_ATT1	0x400267F4	FULL	Master attributes 1
PERI_MS_PPU_FX383_MS_ATT2	0x400267F8	FULL	Master attributes 2
PERI_MS_PPU_FX383_MS_ATT3	0x400267FC	FULL	Master attributes 3

21.401 PPU_FX 384

Register Name	Address	Permission	Description
PERI_MS_PPU_FX384_SL_ADDR	0x40026800	FULL	Slave region, base address
PERI_MS_PPU_FX384_SL_SIZE	0x40026804	FULL	Slave region, size
PERI_MS_PPU_FX384_SL_ATT0	0x40026810	FULL	Slave attributes 0
PERI_MS_PPU_FX384_SL_ATT1	0x40026814	FULL	Slave attributes 1
PERI_MS_PPU_FX384_SL_ATT2	0x40026818	FULL	Slave attributes 2
PERI_MS_PPU_FX384_SL_ATT3	0x4002681C	FULL	Slave attributes 3
PERI_MS_PPU_FX384_MS_ADDR	0x40026820	FULL	Master region, base address
PERI_MS_PPU_FX384_MS_SIZE	0x40026824	FULL	Master region, size
PERI_MS_PPU_FX384_MS_ATT0	0x40026830	FULL	Master attributes 0
PERI_MS_PPU_FX384_MS_ATT1	0x40026834	FULL	Master attributes 1
PERI_MS_PPU_FX384_MS_ATT2	0x40026838	FULL	Master attributes 2
PERI_MS_PPU_FX384_MS_ATT3	0x4002683C	FULL	Master attributes 3

21.402 PPU_FX 385

Register Name	Address	Permission	Description
PERI_MS_PPU_FX385_SL_ADDR	0x40026840	FULL	Slave region, base address
PERI_MS_PPU_FX385_SL_SIZE	0x40026844	FULL	Slave region, size
PERI_MS_PPU_FX385_SL_ATT0	0x40026850	FULL	Slave attributes 0
PERI_MS_PPU_FX385_SL_ATT1	0x40026854	FULL	Slave attributes 1
PERI_MS_PPU_FX385_SL_ATT2	0x40026858	FULL	Slave attributes 2
PERI_MS_PPU_FX385_SL_ATT3	0x4002685C	FULL	Slave attributes 3
PERI_MS_PPU_FX385_MS_ADDR	0x40026860	FULL	Master region, base address
PERI_MS_PPU_FX385_MS_SIZE	0x40026864	FULL	Master region, size
PERI_MS_PPU_FX385_MS_ATT0	0x40026870	FULL	Master attributes 0
PERI_MS_PPU_FX385_MS_ATT1	0x40026874	FULL	Master attributes 1
PERI_MS_PPU_FX385_MS_ATT2	0x40026878	FULL	Master attributes 2
PERI_MS_PPU_FX385_MS_ATT3	0x4002687C	FULL	Master attributes 3

21.403 PPU_FX 386

Register Name	Address	Permission	Description
PERI_MS_PPU_FX386_SL_ADDR	0x40026880	FULL	Slave region, base address
PERI_MS_PPU_FX386_SL_SIZE	0x40026884	FULL	Slave region, size
PERI_MS_PPU_FX386_SL_ATT0	0x40026890	FULL	Slave attributes 0
PERI_MS_PPU_FX386_SL_ATT1	0x40026894	FULL	Slave attributes 1
PERI_MS_PPU_FX386_SL_ATT2	0x40026898	FULL	Slave attributes 2
PERI_MS_PPU_FX386_SL_ATT3	0x4002689C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX386_MS_ADDR	0x400268A0	FULL	Master region, base address
PERI_MS_PPU_FX386_MS_SIZE	0x400268A4	FULL	Master region, size
PERI_MS_PPU_FX386_MS_ATT0	0x400268B0	FULL	Master attributes 0
PERI_MS_PPU_FX386_MS_ATT1	0x400268B4	FULL	Master attributes 1
PERI_MS_PPU_FX386_MS_ATT2	0x400268B8	FULL	Master attributes 2
PERI_MS_PPU_FX386_MS_ATT3	0x400268BC	FULL	Master attributes 3

21.404 PPU_FX 387

Register Name	Address	Permission	Description
PERI_MS_PPU_FX387_SL_ADDR	0x400268C0	FULL	Slave region, base address
PERI_MS_PPU_FX387_SL_SIZE	0x400268C4	FULL	Slave region, size
PERI_MS_PPU_FX387_SL_ATT0	0x400268D0	FULL	Slave attributes 0
PERI_MS_PPU_FX387_SL_ATT1	0x400268D4	FULL	Slave attributes 1
PERI_MS_PPU_FX387_SL_ATT2	0x400268D8	FULL	Slave attributes 2
PERI_MS_PPU_FX387_SL_ATT3	0x400268DC	FULL	Slave attributes 3
PERI_MS_PPU_FX387_MS_ADDR	0x400268E0	FULL	Master region, base address
PERI_MS_PPU_FX387_MS_SIZE	0x400268E4	FULL	Master region, size
PERI_MS_PPU_FX387_MS_ATT0	0x400268F0	FULL	Master attributes 0
PERI_MS_PPU_FX387_MS_ATT1	0x400268F4	FULL	Master attributes 1
PERI_MS_PPU_FX387_MS_ATT2	0x400268F8	FULL	Master attributes 2
PERI_MS_PPU_FX387_MS_ATT3	0x400268FC	FULL	Master attributes 3

21.405 PPU_FX 388

Register Name	Address	Permission	Description
PERI_MS_PPU_FX388_SL_ADDR	0x40026900	FULL	Slave region, base address
PERI_MS_PPU_FX388_SL_SIZE	0x40026904	FULL	Slave region, size
PERI_MS_PPU_FX388_SL_ATT0	0x40026910	FULL	Slave attributes 0
PERI_MS_PPU_FX388_SL_ATT1	0x40026914	FULL	Slave attributes 1
PERI_MS_PPU_FX388_SL_ATT2	0x40026918	FULL	Slave attributes 2
PERI_MS_PPU_FX388_SL_ATT3	0x4002691C	FULL	Slave attributes 3
PERI_MS_PPU_FX388_MS_ADDR	0x40026920	FULL	Master region, base address
PERI_MS_PPU_FX388_MS_SIZE	0x40026924	FULL	Master region, size
PERI_MS_PPU_FX388_MS_ATT0	0x40026930	FULL	Master attributes 0
PERI_MS_PPU_FX388_MS_ATT1	0x40026934	FULL	Master attributes 1
PERI_MS_PPU_FX388_MS_ATT2	0x40026938	FULL	Master attributes 2
PERI_MS_PPU_FX388_MS_ATT3	0x4002693C	FULL	Master attributes 3

21.406 PPU_FX 389

Register Name	Address	Permission	Description
PERI_MS_PPU_FX389_SL_ADDR	0x40026940	FULL	Slave region, base address
PERI_MS_PPU_FX389_SL_SIZE	0x40026944	FULL	Slave region, size
PERI_MS_PPU_FX389_SL_ATT0	0x40026950	FULL	Slave attributes 0
PERI_MS_PPU_FX389_SL_ATT1	0x40026954	FULL	Slave attributes 1
PERI_MS_PPU_FX389_SL_ATT2	0x40026958	FULL	Slave attributes 2
PERI_MS_PPU_FX389_SL_ATT3	0x4002695C	FULL	Slave attributes 3
PERI_MS_PPU_FX389_MS_ADDR	0x40026960	FULL	Master region, base address
PERI_MS_PPU_FX389_MS_SIZE	0x40026964	FULL	Master region, size
PERI_MS_PPU_FX389_MS_ATT0	0x40026970	FULL	Master attributes 0
PERI_MS_PPU_FX389_MS_ATT1	0x40026974	FULL	Master attributes 1
PERI_MS_PPU_FX389_MS_ATT2	0x40026978	FULL	Master attributes 2
PERI_MS_PPU_FX389_MS_ATT3	0x4002697C	FULL	Master attributes 3

21.407 PPU_FX 390

Register Name	Address	Permission	Description
PERI_MS_PPU_FX390_SL_ADDR	0x40026980	FULL	Slave region, base address
PERI_MS_PPU_FX390_SL_SIZE	0x40026984	FULL	Slave region, size
PERI_MS_PPU_FX390_SL_ATT0	0x40026990	FULL	Slave attributes 0
PERI_MS_PPU_FX390_SL_ATT1	0x40026994	FULL	Slave attributes 1
PERI_MS_PPU_FX390_SL_ATT2	0x40026998	FULL	Slave attributes 2
PERI_MS_PPU_FX390_SL_ATT3	0x4002699C	FULL	Slave attributes 3
PERI_MS_PPU_FX390_MS_ADDR	0x400269A0	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX390_MS_SIZE	0x400269A4	FULL	Master region, size
PERI_MS_PPU_FX390_MS_ATT0	0x400269B0	FULL	Master attributes 0
PERI_MS_PPU_FX390_MS_ATT1	0x400269B4	FULL	Master attributes 1
PERI_MS_PPU_FX390_MS_ATT2	0x400269B8	FULL	Master attributes 2
PERI_MS_PPU_FX390_MS_ATT3	0x400269BC	FULL	Master attributes 3

21.408 PPU_FX 391

Register Name	Address	Permission	Description
PERI_MS_PPU_FX391_SL_ADDR	0x400269C0	FULL	Slave region, base address
PERI_MS_PPU_FX391_SL_SIZE	0x400269C4	FULL	Slave region, size
PERI_MS_PPU_FX391_SL_ATT0	0x400269D0	FULL	Slave attributes 0
PERI_MS_PPU_FX391_SL_ATT1	0x400269D4	FULL	Slave attributes 1
PERI_MS_PPU_FX391_SL_ATT2	0x400269D8	FULL	Slave attributes 2
PERI_MS_PPU_FX391_SL_ATT3	0x400269DC	FULL	Slave attributes 3
PERI_MS_PPU_FX391_MS_ADDR	0x400269E0	FULL	Master region, base address
PERI_MS_PPU_FX391_MS_SIZE	0x400269E4	FULL	Master region, size
PERI_MS_PPU_FX391_MS_ATT0	0x400269F0	FULL	Master attributes 0
PERI_MS_PPU_FX391_MS_ATT1	0x400269F4	FULL	Master attributes 1
PERI_MS_PPU_FX391_MS_ATT2	0x400269F8	FULL	Master attributes 2
PERI_MS_PPU_FX391_MS_ATT3	0x400269FC	FULL	Master attributes 3

21.409 PPU_FX 392

Register Name	Address	Permission	Description
PERI_MS_PPU_FX392_SL_ADDR	0x40026A00	FULL	Slave region, base address
PERI_MS_PPU_FX392_SL_SIZE	0x40026A04	FULL	Slave region, size
PERI_MS_PPU_FX392_SL_ATT0	0x40026A10	FULL	Slave attributes 0
PERI_MS_PPU_FX392_SL_ATT1	0x40026A14	FULL	Slave attributes 1
PERI_MS_PPU_FX392_SL_ATT2	0x40026A18	FULL	Slave attributes 2
PERI_MS_PPU_FX392_SL_ATT3	0x40026A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX392_MS_ADDR	0x40026A20	FULL	Master region, base address
PERI_MS_PPU_FX392_MS_SIZE	0x40026A24	FULL	Master region, size
PERI_MS_PPU_FX392_MS_ATT0	0x40026A30	FULL	Master attributes 0
PERI_MS_PPU_FX392_MS_ATT1	0x40026A34	FULL	Master attributes 1
PERI_MS_PPU_FX392_MS_ATT2	0x40026A38	FULL	Master attributes 2
PERI_MS_PPU_FX392_MS_ATT3	0x40026A3C	FULL	Master attributes 3

21.410 PPU_FX 393

Register Name	Address	Permission	Description
PERI_MS_PPU_FX393_SL_ADDR	0x40026A40	FULL	Slave region, base address
PERI_MS_PPU_FX393_SL_SIZE	0x40026A44	FULL	Slave region, size
PERI_MS_PPU_FX393_SL_ATT0	0x40026A50	FULL	Slave attributes 0
PERI_MS_PPU_FX393_SL_ATT1	0x40026A54	FULL	Slave attributes 1
PERI_MS_PPU_FX393_SL_ATT2	0x40026A58	FULL	Slave attributes 2
PERI_MS_PPU_FX393_SL_ATT3	0x40026A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX393_MS_ADDR	0x40026A60	FULL	Master region, base address
PERI_MS_PPU_FX393_MS_SIZE	0x40026A64	FULL	Master region, size
PERI_MS_PPU_FX393_MS_ATT0	0x40026A70	FULL	Master attributes 0
PERI_MS_PPU_FX393_MS_ATT1	0x40026A74	FULL	Master attributes 1
PERI_MS_PPU_FX393_MS_ATT2	0x40026A78	FULL	Master attributes 2
PERI_MS_PPU_FX393_MS_ATT3	0x40026A7C	FULL	Master attributes 3

21.411 PPU_FX 394

Register Name	Address	Permission	Description
PERI_MS_PPU_FX394_SL_ADDR	0x40026A80	FULL	Slave region, base address
PERI_MS_PPU_FX394_SL_SIZE	0x40026A84	FULL	Slave region, size
PERI_MS_PPU_FX394_SL_ATT0	0x40026A90	FULL	Slave attributes 0
PERI_MS_PPU_FX394_SL_ATT1	0x40026A94	FULL	Slave attributes 1
PERI_MS_PPU_FX394_SL_ATT2	0x40026A98	FULL	Slave attributes 2
PERI_MS_PPU_FX394_SL_ATT3	0x40026A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX394_MS_ADDR	0x40026AA0	FULL	Master region, base address
PERI_MS_PPU_FX394_MS_SIZE	0x40026AA4	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX394_MS_ATT0	0x40026AB0	FULL	Master attributes 0
PERI_MS_PPU_FX394_MS_ATT1	0x40026AB4	FULL	Master attributes 1
PERI_MS_PPU_FX394_MS_ATT2	0x40026AB8	FULL	Master attributes 2
PERI_MS_PPU_FX394_MS_ATT3	0x40026ABC	FULL	Master attributes 3

21.412 PPU_FX 395

Register Name	Address	Permission	Description
PERI_MS_PPU_FX395_SL_ADDR	0x40026AC0	FULL	Slave region, base address
PERI_MS_PPU_FX395_SL_SIZE	0x40026AC4	FULL	Slave region, size
PERI_MS_PPU_FX395_SL_ATT0	0x40026AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX395_SL_ATT1	0x40026AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX395_SL_ATT2	0x40026AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX395_SL_ATT3	0x40026ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX395_MS_ADDR	0x40026AE0	FULL	Master region, base address
PERI_MS_PPU_FX395_MS_SIZE	0x40026AE4	FULL	Master region, size
PERI_MS_PPU_FX395_MS_ATT0	0x40026AF0	FULL	Master attributes 0
PERI_MS_PPU_FX395_MS_ATT1	0x40026AF4	FULL	Master attributes 1
PERI_MS_PPU_FX395_MS_ATT2	0x40026AF8	FULL	Master attributes 2
PERI_MS_PPU_FX395_MS_ATT3	0x40026AFC	FULL	Master attributes 3

21.413 PPU_FX 396

Register Name	Address	Permission	Description
PERI_MS_PPU_FX396_SL_ADDR	0x40026B00	FULL	Slave region, base address
PERI_MS_PPU_FX396_SL_SIZE	0x40026B04	FULL	Slave region, size
PERI_MS_PPU_FX396_SL_ATT0	0x40026B10	FULL	Slave attributes 0
PERI_MS_PPU_FX396_SL_ATT1	0x40026B14	FULL	Slave attributes 1
PERI_MS_PPU_FX396_SL_ATT2	0x40026B18	FULL	Slave attributes 2
PERI_MS_PPU_FX396_SL_ATT3	0x40026B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX396_MS_ADDR	0x40026B20	FULL	Master region, base address
PERI_MS_PPU_FX396_MS_SIZE	0x40026B24	FULL	Master region, size
PERI_MS_PPU_FX396_MS_ATT0	0x40026B30	FULL	Master attributes 0
PERI_MS_PPU_FX396_MS_ATT1	0x40026B34	FULL	Master attributes 1
PERI_MS_PPU_FX396_MS_ATT2	0x40026B38	FULL	Master attributes 2
PERI_MS_PPU_FX396_MS_ATT3	0x40026B3C	FULL	Master attributes 3

21.414 PPU_FX 397

Register Name	Address	Permission	Description
PERI_MS_PPU_FX397_SL_ADDR	0x40026B40	FULL	Slave region, base address
PERI_MS_PPU_FX397_SL_SIZE	0x40026B44	FULL	Slave region, size
PERI_MS_PPU_FX397_SL_ATT0	0x40026B50	FULL	Slave attributes 0
PERI_MS_PPU_FX397_SL_ATT1	0x40026B54	FULL	Slave attributes 1
PERI_MS_PPU_FX397_SL_ATT2	0x40026B58	FULL	Slave attributes 2
PERI_MS_PPU_FX397_SL_ATT3	0x40026B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX397_MS_ADDR	0x40026B60	FULL	Master region, base address
PERI_MS_PPU_FX397_MS_SIZE	0x40026B64	FULL	Master region, size
PERI_MS_PPU_FX397_MS_ATT0	0x40026B70	FULL	Master attributes 0
PERI_MS_PPU_FX397_MS_ATT1	0x40026B74	FULL	Master attributes 1
PERI_MS_PPU_FX397_MS_ATT2	0x40026B78	FULL	Master attributes 2
PERI_MS_PPU_FX397_MS_ATT3	0x40026B7C	FULL	Master attributes 3

21.415 PPU_FX 398

Register Name	Address	Permission	Description
PERI_MS_PPU_FX398_SL_ADDR	0x40026B80	FULL	Slave region, base address
PERI_MS_PPU_FX398_SL_SIZE	0x40026B84	FULL	Slave region, size
PERI_MS_PPU_FX398_SL_ATT0	0x40026B90	FULL	Slave attributes 0
PERI_MS_PPU_FX398_SL_ATT1	0x40026B94	FULL	Slave attributes 1
PERI_MS_PPU_FX398_SL_ATT2	0x40026B98	FULL	Slave attributes 2
PERI_MS_PPU_FX398_SL_ATT3	0x40026B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX398_MS_ADDR	0x40026BA0	FULL	Master region, base address
PERI_MS_PPU_FX398_MS_SIZE	0x40026BA4	FULL	Master region, size
PERI_MS_PPU_FX398_MS_ATT0	0x40026BB0	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX398_MS_ATT1	0x40026BB4	FULL	Master attributes 1
PERI_MS_PPU_FX398_MS_ATT2	0x40026BB8	FULL	Master attributes 2
PERI_MS_PPU_FX398_MS_ATT3	0x40026BBC	FULL	Master attributes 3

21.416 PPU_FX 399

Register Name	Address	Permission	Description
PERI_MS_PPU_FX399_SL_ADDR	0x40026BC0	FULL	Slave region, base address
PERI_MS_PPU_FX399_SL_SIZE	0x40026BC4	FULL	Slave region, size
PERI_MS_PPU_FX399_SL_ATT0	0x40026BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX399_SL_ATT1	0x40026BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX399_SL_ATT2	0x40026BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX399_SL_ATT3	0x40026BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX399_MS_ADDR	0x40026BE0	FULL	Master region, base address
PERI_MS_PPU_FX399_MS_SIZE	0x40026BE4	FULL	Master region, size
PERI_MS_PPU_FX399_MS_ATT0	0x40026BF0	FULL	Master attributes 0
PERI_MS_PPU_FX399_MS_ATT1	0x40026BF4	FULL	Master attributes 1
PERI_MS_PPU_FX399_MS_ATT2	0x40026BF8	FULL	Master attributes 2
PERI_MS_PPU_FX399_MS_ATT3	0x40026BFC	FULL	Master attributes 3

21.417 PPU_FX 400

Register Name	Address	Permission	Description
PERI_MS_PPU_FX400_SL_ADDR	0x40026C00	FULL	Slave region, base address
PERI_MS_PPU_FX400_SL_SIZE	0x40026C04	FULL	Slave region, size
PERI_MS_PPU_FX400_SL_ATT0	0x40026C10	FULL	Slave attributes 0
PERI_MS_PPU_FX400_SL_ATT1	0x40026C14	FULL	Slave attributes 1
PERI_MS_PPU_FX400_SL_ATT2	0x40026C18	FULL	Slave attributes 2
PERI_MS_PPU_FX400_SL_ATT3	0x40026C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX400_MS_ADDR	0x40026C20	FULL	Master region, base address
PERI_MS_PPU_FX400_MS_SIZE	0x40026C24	FULL	Master region, size
PERI_MS_PPU_FX400_MS_ATT0	0x40026C30	FULL	Master attributes 0
PERI_MS_PPU_FX400_MS_ATT1	0x40026C34	FULL	Master attributes 1
PERI_MS_PPU_FX400_MS_ATT2	0x40026C38	FULL	Master attributes 2
PERI_MS_PPU_FX400_MS_ATT3	0x40026C3C	FULL	Master attributes 3

21.418 PPU_FX 401

Register Name	Address	Permission	Description
PERI_MS_PPU_FX401_SL_ADDR	0x40026C40	FULL	Slave region, base address
PERI_MS_PPU_FX401_SL_SIZE	0x40026C44	FULL	Slave region, size
PERI_MS_PPU_FX401_SL_ATT0	0x40026C50	FULL	Slave attributes 0
PERI_MS_PPU_FX401_SL_ATT1	0x40026C54	FULL	Slave attributes 1
PERI_MS_PPU_FX401_SL_ATT2	0x40026C58	FULL	Slave attributes 2
PERI_MS_PPU_FX401_SL_ATT3	0x40026C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX401_MS_ADDR	0x40026C60	FULL	Master region, base address
PERI_MS_PPU_FX401_MS_SIZE	0x40026C64	FULL	Master region, size
PERI_MS_PPU_FX401_MS_ATT0	0x40026C70	FULL	Master attributes 0
PERI_MS_PPU_FX401_MS_ATT1	0x40026C74	FULL	Master attributes 1
PERI_MS_PPU_FX401_MS_ATT2	0x40026C78	FULL	Master attributes 2
PERI_MS_PPU_FX401_MS_ATT3	0x40026C7C	FULL	Master attributes 3

21.419 PPU_FX 402

Register Name	Address	Permission	Description
PERI_MS_PPU_FX402_SL_ADDR	0x40026C80	FULL	Slave region, base address
PERI_MS_PPU_FX402_SL_SIZE	0x40026C84	FULL	Slave region, size
PERI_MS_PPU_FX402_SL_ATT0	0x40026C90	FULL	Slave attributes 0
PERI_MS_PPU_FX402_SL_ATT1	0x40026C94	FULL	Slave attributes 1
PERI_MS_PPU_FX402_SL_ATT2	0x40026C98	FULL	Slave attributes 2
PERI_MS_PPU_FX402_SL_ATT3	0x40026C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX402_MS_ADDR	0x40026CA0	FULL	Master region, base address
PERI_MS_PPU_FX402_MS_SIZE	0x40026CA4	FULL	Master region, size
PERI_MS_PPU_FX402_MS_ATT0	0x40026CB0	FULL	Master attributes 0
PERI_MS_PPU_FX402_MS_ATT1	0x40026CB4	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX402_MS_ATT2	0x40026CB8	FULL	Master attributes 2
PERI_MS_PPU_FX402_MS_ATT3	0x40026CBC	FULL	Master attributes 3

21.420 PPU_FX 403

Register Name	Address	Permission	Description
PERI_MS_PPU_FX403_SL_ADDR	0x40026CC0	FULL	Slave region, base address
PERI_MS_PPU_FX403_SL_SIZE	0x40026CC4	FULL	Slave region, size
PERI_MS_PPU_FX403_SL_ATT0	0x40026CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX403_SL_ATT1	0x40026CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX403_SL_ATT2	0x40026CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX403_SL_ATT3	0x40026CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX403_MS_ADDR	0x40026CE0	FULL	Master region, base address
PERI_MS_PPU_FX403_MS_SIZE	0x40026CE4	FULL	Master region, size
PERI_MS_PPU_FX403_MS_ATT0	0x40026CF0	FULL	Master attributes 0
PERI_MS_PPU_FX403_MS_ATT1	0x40026CF4	FULL	Master attributes 1
PERI_MS_PPU_FX403_MS_ATT2	0x40026CF8	FULL	Master attributes 2
PERI_MS_PPU_FX403_MS_ATT3	0x40026CFC	FULL	Master attributes 3

21.421 PPU_FX 404

Register Name	Address	Permission	Description
PERI_MS_PPU_FX404_SL_ADDR	0x40026D00	FULL	Slave region, base address
PERI_MS_PPU_FX404_SL_SIZE	0x40026D04	FULL	Slave region, size
PERI_MS_PPU_FX404_SL_ATT0	0x40026D10	FULL	Slave attributes 0
PERI_MS_PPU_FX404_SL_ATT1	0x40026D14	FULL	Slave attributes 1
PERI_MS_PPU_FX404_SL_ATT2	0x40026D18	FULL	Slave attributes 2
PERI_MS_PPU_FX404_SL_ATT3	0x40026D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX404_MS_ADDR	0x40026D20	FULL	Master region, base address
PERI_MS_PPU_FX404_MS_SIZE	0x40026D24	FULL	Master region, size
PERI_MS_PPU_FX404_MS_ATT0	0x40026D30	FULL	Master attributes 0
PERI_MS_PPU_FX404_MS_ATT1	0x40026D34	FULL	Master attributes 1
PERI_MS_PPU_FX404_MS_ATT2	0x40026D38	FULL	Master attributes 2
PERI_MS_PPU_FX404_MS_ATT3	0x40026D3C	FULL	Master attributes 3

21.422 PPU_FX 405

Register Name	Address	Permission	Description
PERI_MS_PPU_FX405_SL_ADDR	0x40026D40	FULL	Slave region, base address
PERI_MS_PPU_FX405_SL_SIZE	0x40026D44	FULL	Slave region, size
PERI_MS_PPU_FX405_SL_ATT0	0x40026D50	FULL	Slave attributes 0
PERI_MS_PPU_FX405_SL_ATT1	0x40026D54	FULL	Slave attributes 1
PERI_MS_PPU_FX405_SL_ATT2	0x40026D58	FULL	Slave attributes 2
PERI_MS_PPU_FX405_SL_ATT3	0x40026D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX405_MS_ADDR	0x40026D60	FULL	Master region, base address
PERI_MS_PPU_FX405_MS_SIZE	0x40026D64	FULL	Master region, size
PERI_MS_PPU_FX405_MS_ATT0	0x40026D70	FULL	Master attributes 0
PERI_MS_PPU_FX405_MS_ATT1	0x40026D74	FULL	Master attributes 1
PERI_MS_PPU_FX405_MS_ATT2	0x40026D78	FULL	Master attributes 2
PERI_MS_PPU_FX405_MS_ATT3	0x40026D7C	FULL	Master attributes 3

21.423 PPU_FX 406

Register Name	Address	Permission	Description
PERI_MS_PPU_FX406_SL_ADDR	0x40026D80	FULL	Slave region, base address
PERI_MS_PPU_FX406_SL_SIZE	0x40026D84	FULL	Slave region, size
PERI_MS_PPU_FX406_SL_ATT0	0x40026D90	FULL	Slave attributes 0
PERI_MS_PPU_FX406_SL_ATT1	0x40026D94	FULL	Slave attributes 1
PERI_MS_PPU_FX406_SL_ATT2	0x40026D98	FULL	Slave attributes 2
PERI_MS_PPU_FX406_SL_ATT3	0x40026D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX406_MS_ADDR	0x40026DA0	FULL	Master region, base address
PERI_MS_PPU_FX406_MS_SIZE	0x40026DA4	FULL	Master region, size
PERI_MS_PPU_FX406_MS_ATT0	0x40026DB0	FULL	Master attributes 0
PERI_MS_PPU_FX406_MS_ATT1	0x40026DB4	FULL	Master attributes 1
PERI_MS_PPU_FX406_MS_ATT2	0x40026DB8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX406_MS_ATT3	0x40026DBC	FULL	Master attributes 3

21.424 PPU_FX 407

Register Name	Address	Permission	Description
PERI_MS_PPU_FX407_SL_ADDR	0x40026DC0	FULL	Slave region, base address
PERI_MS_PPU_FX407_SL_SIZE	0x40026DC4	FULL	Slave region, size
PERI_MS_PPU_FX407_SL_ATT0	0x40026DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX407_SL_ATT1	0x40026DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX407_SL_ATT2	0x40026DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX407_SL_ATT3	0x40026DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX407_MS_ADDR	0x40026DE0	FULL	Master region, base address
PERI_MS_PPU_FX407_MS_SIZE	0x40026DE4	FULL	Master region, size
PERI_MS_PPU_FX407_MS_ATT0	0x40026DF0	FULL	Master attributes 0
PERI_MS_PPU_FX407_MS_ATT1	0x40026DF4	FULL	Master attributes 1
PERI_MS_PPU_FX407_MS_ATT2	0x40026DF8	FULL	Master attributes 2
PERI_MS_PPU_FX407_MS_ATT3	0x40026DFC	FULL	Master attributes 3

21.425 PPU_FX 408

Register Name	Address	Permission	Description
PERI_MS_PPU_FX408_SL_ADDR	0x40026E00	FULL	Slave region, base address
PERI_MS_PPU_FX408_SL_SIZE	0x40026E04	FULL	Slave region, size
PERI_MS_PPU_FX408_SL_ATT0	0x40026E10	FULL	Slave attributes 0
PERI_MS_PPU_FX408_SL_ATT1	0x40026E14	FULL	Slave attributes 1
PERI_MS_PPU_FX408_SL_ATT2	0x40026E18	FULL	Slave attributes 2
PERI_MS_PPU_FX408_SL_ATT3	0x40026E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX408_MS_ADDR	0x40026E20	FULL	Master region, base address
PERI_MS_PPU_FX408_MS_SIZE	0x40026E24	FULL	Master region, size
PERI_MS_PPU_FX408_MS_ATT0	0x40026E30	FULL	Master attributes 0
PERI_MS_PPU_FX408_MS_ATT1	0x40026E34	FULL	Master attributes 1
PERI_MS_PPU_FX408_MS_ATT2	0x40026E38	FULL	Master attributes 2
PERI_MS_PPU_FX408_MS_ATT3	0x40026E3C	FULL	Master attributes 3

21.426 PPU_FX 409

Register Name	Address	Permission	Description
PERI_MS_PPU_FX409_SL_ADDR	0x40026E40	FULL	Slave region, base address
PERI_MS_PPU_FX409_SL_SIZE	0x40026E44	FULL	Slave region, size
PERI_MS_PPU_FX409_SL_ATT0	0x40026E50	FULL	Slave attributes 0
PERI_MS_PPU_FX409_SL_ATT1	0x40026E54	FULL	Slave attributes 1
PERI_MS_PPU_FX409_SL_ATT2	0x40026E58	FULL	Slave attributes 2
PERI_MS_PPU_FX409_SL_ATT3	0x40026E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX409_MS_ADDR	0x40026E60	FULL	Master region, base address
PERI_MS_PPU_FX409_MS_SIZE	0x40026E64	FULL	Master region, size
PERI_MS_PPU_FX409_MS_ATT0	0x40026E70	FULL	Master attributes 0
PERI_MS_PPU_FX409_MS_ATT1	0x40026E74	FULL	Master attributes 1
PERI_MS_PPU_FX409_MS_ATT2	0x40026E78	FULL	Master attributes 2
PERI_MS_PPU_FX409_MS_ATT3	0x40026E7C	FULL	Master attributes 3

21.427 PPU_FX 410

Register Name	Address	Permission	Description
PERI_MS_PPU_FX410_SL_ADDR	0x40026E80	FULL	Slave region, base address
PERI_MS_PPU_FX410_SL_SIZE	0x40026E84	FULL	Slave region, size
PERI_MS_PPU_FX410_SL_ATT0	0x40026E90	FULL	Slave attributes 0
PERI_MS_PPU_FX410_SL_ATT1	0x40026E94	FULL	Slave attributes 1
PERI_MS_PPU_FX410_SL_ATT2	0x40026E98	FULL	Slave attributes 2
PERI_MS_PPU_FX410_SL_ATT3	0x40026E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX410_MS_ADDR	0x40026EA0	FULL	Master region, base address
PERI_MS_PPU_FX410_MS_SIZE	0x40026EA4	FULL	Master region, size
PERI_MS_PPU_FX410_MS_ATT0	0x40026EB0	FULL	Master attributes 0
PERI_MS_PPU_FX410_MS_ATT1	0x40026EB4	FULL	Master attributes 1
PERI_MS_PPU_FX410_MS_ATT2	0x40026EB8	FULL	Master attributes 2
PERI_MS_PPU_FX410_MS_ATT3	0x40026EBC	FULL	Master attributes 3

21.428 PPU_FX 411

Register Name	Address	Permission	Description
PERI_MS_PPU_FX411_SL_ADDR	0x40026EC0	FULL	Slave region, base address
PERI_MS_PPU_FX411_SL_SIZE	0x40026EC4	FULL	Slave region, size
PERI_MS_PPU_FX411_SL_ATT0	0x40026ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX411_SL_ATT1	0x40026ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX411_SL_ATT2	0x40026ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX411_SL_ATT3	0x40026EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX411_MS_ADDR	0x40026EE0	FULL	Master region, base address
PERI_MS_PPU_FX411_MS_SIZE	0x40026EE4	FULL	Master region, size
PERI_MS_PPU_FX411_MS_ATT0	0x40026EF0	FULL	Master attributes 0
PERI_MS_PPU_FX411_MS_ATT1	0x40026EF4	FULL	Master attributes 1
PERI_MS_PPU_FX411_MS_ATT2	0x40026EF8	FULL	Master attributes 2
PERI_MS_PPU_FX411_MS_ATT3	0x40026EFC	FULL	Master attributes 3

21.429 PPU_FX 412

Register Name	Address	Permission	Description
PERI_MS_PPU_FX412_SL_ADDR	0x40026F00	FULL	Slave region, base address
PERI_MS_PPU_FX412_SL_SIZE	0x40026F04	FULL	Slave region, size
PERI_MS_PPU_FX412_SL_ATT0	0x40026F10	FULL	Slave attributes 0
PERI_MS_PPU_FX412_SL_ATT1	0x40026F14	FULL	Slave attributes 1
PERI_MS_PPU_FX412_SL_ATT2	0x40026F18	FULL	Slave attributes 2
PERI_MS_PPU_FX412_SL_ATT3	0x40026F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX412_MS_ADDR	0x40026F20	FULL	Master region, base address
PERI_MS_PPU_FX412_MS_SIZE	0x40026F24	FULL	Master region, size
PERI_MS_PPU_FX412_MS_ATT0	0x40026F30	FULL	Master attributes 0
PERI_MS_PPU_FX412_MS_ATT1	0x40026F34	FULL	Master attributes 1
PERI_MS_PPU_FX412_MS_ATT2	0x40026F38	FULL	Master attributes 2
PERI_MS_PPU_FX412_MS_ATT3	0x40026F3C	FULL	Master attributes 3

21.430 PPU_FX 413

Register Name	Address	Permission	Description
PERI_MS_PPU_FX413_SL_ADDR	0x40026F40	FULL	Slave region, base address
PERI_MS_PPU_FX413_SL_SIZE	0x40026F44	FULL	Slave region, size
PERI_MS_PPU_FX413_SL_ATT0	0x40026F50	FULL	Slave attributes 0
PERI_MS_PPU_FX413_SL_ATT1	0x40026F54	FULL	Slave attributes 1
PERI_MS_PPU_FX413_SL_ATT2	0x40026F58	FULL	Slave attributes 2
PERI_MS_PPU_FX413_SL_ATT3	0x40026F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX413_MS_ADDR	0x40026F60	FULL	Master region, base address
PERI_MS_PPU_FX413_MS_SIZE	0x40026F64	FULL	Master region, size
PERI_MS_PPU_FX413_MS_ATT0	0x40026F70	FULL	Master attributes 0
PERI_MS_PPU_FX413_MS_ATT1	0x40026F74	FULL	Master attributes 1
PERI_MS_PPU_FX413_MS_ATT2	0x40026F78	FULL	Master attributes 2
PERI_MS_PPU_FX413_MS_ATT3	0x40026F7C	FULL	Master attributes 3

21.431 PPU_FX 414

Register Name	Address	Permission	Description
PERI_MS_PPU_FX414_SL_ADDR	0x40026F80	FULL	Slave region, base address
PERI_MS_PPU_FX414_SL_SIZE	0x40026F84	FULL	Slave region, size
PERI_MS_PPU_FX414_SL_ATT0	0x40026F90	FULL	Slave attributes 0
PERI_MS_PPU_FX414_SL_ATT1	0x40026F94	FULL	Slave attributes 1
PERI_MS_PPU_FX414_SL_ATT2	0x40026F98	FULL	Slave attributes 2
PERI_MS_PPU_FX414_SL_ATT3	0x40026F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX414_MS_ADDR	0x40026FA0	FULL	Master region, base address
PERI_MS_PPU_FX414_MS_SIZE	0x40026FA4	FULL	Master region, size
PERI_MS_PPU_FX414_MS_ATT0	0x40026FB0	FULL	Master attributes 0
PERI_MS_PPU_FX414_MS_ATT1	0x40026FB4	FULL	Master attributes 1
PERI_MS_PPU_FX414_MS_ATT2	0x40026FB8	FULL	Master attributes 2
PERI_MS_PPU_FX414_MS_ATT3	0x40026FBC	FULL	Master attributes 3

21.432 PPU_FX 415

Register Name	Address	Permission	Description
PERI_MS_PPU_FX415_SL_ADDR	0x40026FC0	FULL	Slave region, base address
PERI_MS_PPU_FX415_SL_SIZE	0x40026FC4	FULL	Slave region, size
PERI_MS_PPU_FX415_SL_ATT0	0x40026FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX415_SL_ATT1	0x40026FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX415_SL_ATT2	0x40026FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX415_SL_ATT3	0x40026FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX415_MS_ADDR	0x40026FE0	FULL	Master region, base address
PERI_MS_PPU_FX415_MS_SIZE	0x40026FE4	FULL	Master region, size
PERI_MS_PPU_FX415_MS_ATT0	0x40026FF0	FULL	Master attributes 0
PERI_MS_PPU_FX415_MS_ATT1	0x40026FF4	FULL	Master attributes 1
PERI_MS_PPU_FX415_MS_ATT2	0x40026FF8	FULL	Master attributes 2
PERI_MS_PPU_FX415_MS_ATT3	0x40026FFC	FULL	Master attributes 3

21.433 PPU_FX 416

Register Name	Address	Permission	Description
PERI_MS_PPU_FX416_SL_ADDR	0x40027000	FULL	Slave region, base address
PERI_MS_PPU_FX416_SL_SIZE	0x40027004	FULL	Slave region, size
PERI_MS_PPU_FX416_SL_ATT0	0x40027010	FULL	Slave attributes 0
PERI_MS_PPU_FX416_SL_ATT1	0x40027014	FULL	Slave attributes 1
PERI_MS_PPU_FX416_SL_ATT2	0x40027018	FULL	Slave attributes 2
PERI_MS_PPU_FX416_SL_ATT3	0x4002701C	FULL	Slave attributes 3
PERI_MS_PPU_FX416_MS_ADDR	0x40027020	FULL	Master region, base address
PERI_MS_PPU_FX416_MS_SIZE	0x40027024	FULL	Master region, size
PERI_MS_PPU_FX416_MS_ATT0	0x40027030	FULL	Master attributes 0
PERI_MS_PPU_FX416_MS_ATT1	0x40027034	FULL	Master attributes 1
PERI_MS_PPU_FX416_MS_ATT2	0x40027038	FULL	Master attributes 2
PERI_MS_PPU_FX416_MS_ATT3	0x4002703C	FULL	Master attributes 3

21.434 PPU_FX 417

Register Name	Address	Permission	Description
PERI_MS_PPU_FX417_SL_ADDR	0x40027040	FULL	Slave region, base address
PERI_MS_PPU_FX417_SL_SIZE	0x40027044	FULL	Slave region, size
PERI_MS_PPU_FX417_SL_ATT0	0x40027050	FULL	Slave attributes 0
PERI_MS_PPU_FX417_SL_ATT1	0x40027054	FULL	Slave attributes 1
PERI_MS_PPU_FX417_SL_ATT2	0x40027058	FULL	Slave attributes 2
PERI_MS_PPU_FX417_SL_ATT3	0x4002705C	FULL	Slave attributes 3
PERI_MS_PPU_FX417_MS_ADDR	0x40027060	FULL	Master region, base address
PERI_MS_PPU_FX417_MS_SIZE	0x40027064	FULL	Master region, size
PERI_MS_PPU_FX417_MS_ATT0	0x40027070	FULL	Master attributes 0
PERI_MS_PPU_FX417_MS_ATT1	0x40027074	FULL	Master attributes 1
PERI_MS_PPU_FX417_MS_ATT2	0x40027078	FULL	Master attributes 2
PERI_MS_PPU_FX417_MS_ATT3	0x4002707C	FULL	Master attributes 3

21.435 PPU_FX 418

Register Name	Address	Permission	Description
PERI_MS_PPU_FX418_SL_ADDR	0x40027080	FULL	Slave region, base address
PERI_MS_PPU_FX418_SL_SIZE	0x40027084	FULL	Slave region, size
PERI_MS_PPU_FX418_SL_ATT0	0x40027090	FULL	Slave attributes 0
PERI_MS_PPU_FX418_SL_ATT1	0x40027094	FULL	Slave attributes 1
PERI_MS_PPU_FX418_SL_ATT2	0x40027098	FULL	Slave attributes 2
PERI_MS_PPU_FX418_SL_ATT3	0x4002709C	FULL	Slave attributes 3
PERI_MS_PPU_FX418_MS_ADDR	0x400270A0	FULL	Master region, base address
PERI_MS_PPU_FX418_MS_SIZE	0x400270A4	FULL	Master region, size
PERI_MS_PPU_FX418_MS_ATT0	0x400270B0	FULL	Master attributes 0
PERI_MS_PPU_FX418_MS_ATT1	0x400270B4	FULL	Master attributes 1
PERI_MS_PPU_FX418_MS_ATT2	0x400270B8	FULL	Master attributes 2
PERI_MS_PPU_FX418_MS_ATT3	0x400270BC	FULL	Master attributes 3

21.436 PPU_FX 419

Register Name	Address	Permission	Description
PERI_MS_PPU_FX419_SL_ADDR	0x400270C0	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX419_SL_SIZE	0x400270C4	FULL	Slave region, size
PERI_MS_PPU_FX419_SL_ATT0	0x400270D0	FULL	Slave attributes 0
PERI_MS_PPU_FX419_SL_ATT1	0x400270D4	FULL	Slave attributes 1
PERI_MS_PPU_FX419_SL_ATT2	0x400270D8	FULL	Slave attributes 2
PERI_MS_PPU_FX419_SL_ATT3	0x400270DC	FULL	Slave attributes 3
PERI_MS_PPU_FX419_MS_ADDR	0x400270E0	FULL	Master region, base address
PERI_MS_PPU_FX419_MS_SIZE	0x400270E4	FULL	Master region, size
PERI_MS_PPU_FX419_MS_ATT0	0x400270F0	FULL	Master attributes 0
PERI_MS_PPU_FX419_MS_ATT1	0x400270F4	FULL	Master attributes 1
PERI_MS_PPU_FX419_MS_ATT2	0x400270F8	FULL	Master attributes 2
PERI_MS_PPU_FX419_MS_ATT3	0x400270FC	FULL	Master attributes 3

21.437 PPU_FX 420

Register Name	Address	Permission	Description
PERI_MS_PPU_FX420_SL_ADDR	0x40027100	FULL	Slave region, base address
PERI_MS_PPU_FX420_SL_SIZE	0x40027104	FULL	Slave region, size
PERI_MS_PPU_FX420_SL_ATT0	0x40027110	FULL	Slave attributes 0
PERI_MS_PPU_FX420_SL_ATT1	0x40027114	FULL	Slave attributes 1
PERI_MS_PPU_FX420_SL_ATT2	0x40027118	FULL	Slave attributes 2
PERI_MS_PPU_FX420_SL_ATT3	0x4002711C	FULL	Slave attributes 3
PERI_MS_PPU_FX420_MS_ADDR	0x40027120	FULL	Master region, base address
PERI_MS_PPU_FX420_MS_SIZE	0x40027124	FULL	Master region, size
PERI_MS_PPU_FX420_MS_ATT0	0x40027130	FULL	Master attributes 0
PERI_MS_PPU_FX420_MS_ATT1	0x40027134	FULL	Master attributes 1
PERI_MS_PPU_FX420_MS_ATT2	0x40027138	FULL	Master attributes 2
PERI_MS_PPU_FX420_MS_ATT3	0x4002713C	FULL	Master attributes 3

21.438 PPU_FX 421

Register Name	Address	Permission	Description
PERI_MS_PPU_FX421_SL_ADDR	0x40027140	FULL	Slave region, base address
PERI_MS_PPU_FX421_SL_SIZE	0x40027144	FULL	Slave region, size
PERI_MS_PPU_FX421_SL_ATT0	0x40027150	FULL	Slave attributes 0
PERI_MS_PPU_FX421_SL_ATT1	0x40027154	FULL	Slave attributes 1
PERI_MS_PPU_FX421_SL_ATT2	0x40027158	FULL	Slave attributes 2
PERI_MS_PPU_FX421_SL_ATT3	0x4002715C	FULL	Slave attributes 3
PERI_MS_PPU_FX421_MS_ADDR	0x40027160	FULL	Master region, base address
PERI_MS_PPU_FX421_MS_SIZE	0x40027164	FULL	Master region, size
PERI_MS_PPU_FX421_MS_ATT0	0x40027170	FULL	Master attributes 0
PERI_MS_PPU_FX421_MS_ATT1	0x40027174	FULL	Master attributes 1
PERI_MS_PPU_FX421_MS_ATT2	0x40027178	FULL	Master attributes 2
PERI_MS_PPU_FX421_MS_ATT3	0x4002717C	FULL	Master attributes 3

21.439 PPU_FX 422

Register Name	Address	Permission	Description
PERI_MS_PPU_FX422_SL_ADDR	0x40027180	FULL	Slave region, base address
PERI_MS_PPU_FX422_SL_SIZE	0x40027184	FULL	Slave region, size
PERI_MS_PPU_FX422_SL_ATT0	0x40027190	FULL	Slave attributes 0
PERI_MS_PPU_FX422_SL_ATT1	0x40027194	FULL	Slave attributes 1
PERI_MS_PPU_FX422_SL_ATT2	0x40027198	FULL	Slave attributes 2
PERI_MS_PPU_FX422_SL_ATT3	0x4002719C	FULL	Slave attributes 3
PERI_MS_PPU_FX422_MS_ADDR	0x400271A0	FULL	Master region, base address
PERI_MS_PPU_FX422_MS_SIZE	0x400271A4	FULL	Master region, size
PERI_MS_PPU_FX422_MS_ATT0	0x400271B0	FULL	Master attributes 0
PERI_MS_PPU_FX422_MS_ATT1	0x400271B4	FULL	Master attributes 1
PERI_MS_PPU_FX422_MS_ATT2	0x400271B8	FULL	Master attributes 2
PERI_MS_PPU_FX422_MS_ATT3	0x400271BC	FULL	Master attributes 3

21.440 PPU_FX 423

Register Name	Address	Permission	Description
PERI_MS_PPU_FX423_SL_ADDR	0x400271C0	FULL	Slave region, base address
PERI_MS_PPU_FX423_SL_SIZE	0x400271C4	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX423_SL_ATT0	0x400271D0	FULL	Slave attributes 0
PERI_MS_PPU_FX423_SL_ATT1	0x400271D4	FULL	Slave attributes 1
PERI_MS_PPU_FX423_SL_ATT2	0x400271D8	FULL	Slave attributes 2
PERI_MS_PPU_FX423_SL_ATT3	0x400271DC	FULL	Slave attributes 3
PERI_MS_PPU_FX423_MS_ADDR	0x400271E0	FULL	Master region, base address
PERI_MS_PPU_FX423_MS_SIZE	0x400271E4	FULL	Master region, size
PERI_MS_PPU_FX423_MS_ATT0	0x400271F0	FULL	Master attributes 0
PERI_MS_PPU_FX423_MS_ATT1	0x400271F4	FULL	Master attributes 1
PERI_MS_PPU_FX423_MS_ATT2	0x400271F8	FULL	Master attributes 2
PERI_MS_PPU_FX423_MS_ATT3	0x400271FC	FULL	Master attributes 3

21.441 PPU_FX 424

Register Name	Address	Permission	Description
PERI_MS_PPU_FX424_SL_ADDR	0x40027200	FULL	Slave region, base address
PERI_MS_PPU_FX424_SL_SIZE	0x40027204	FULL	Slave region, size
PERI_MS_PPU_FX424_SL_ATT0	0x40027210	FULL	Slave attributes 0
PERI_MS_PPU_FX424_SL_ATT1	0x40027214	FULL	Slave attributes 1
PERI_MS_PPU_FX424_SL_ATT2	0x40027218	FULL	Slave attributes 2
PERI_MS_PPU_FX424_SL_ATT3	0x4002721C	FULL	Slave attributes 3
PERI_MS_PPU_FX424_MS_ADDR	0x40027220	FULL	Master region, base address
PERI_MS_PPU_FX424_MS_SIZE	0x40027224	FULL	Master region, size
PERI_MS_PPU_FX424_MS_ATT0	0x40027230	FULL	Master attributes 0
PERI_MS_PPU_FX424_MS_ATT1	0x40027234	FULL	Master attributes 1
PERI_MS_PPU_FX424_MS_ATT2	0x40027238	FULL	Master attributes 2
PERI_MS_PPU_FX424_MS_ATT3	0x4002723C	FULL	Master attributes 3

21.442 PPU_FX 425

Register Name	Address	Permission	Description
PERI_MS_PPU_FX425_SL_ADDR	0x40027240	FULL	Slave region, base address
PERI_MS_PPU_FX425_SL_SIZE	0x40027244	FULL	Slave region, size
PERI_MS_PPU_FX425_SL_ATT0	0x40027250	FULL	Slave attributes 0
PERI_MS_PPU_FX425_SL_ATT1	0x40027254	FULL	Slave attributes 1
PERI_MS_PPU_FX425_SL_ATT2	0x40027258	FULL	Slave attributes 2
PERI_MS_PPU_FX425_SL_ATT3	0x4002725C	FULL	Slave attributes 3
PERI_MS_PPU_FX425_MS_ADDR	0x40027260	FULL	Master region, base address
PERI_MS_PPU_FX425_MS_SIZE	0x40027264	FULL	Master region, size
PERI_MS_PPU_FX425_MS_ATT0	0x40027270	FULL	Master attributes 0
PERI_MS_PPU_FX425_MS_ATT1	0x40027274	FULL	Master attributes 1
PERI_MS_PPU_FX425_MS_ATT2	0x40027278	FULL	Master attributes 2
PERI_MS_PPU_FX425_MS_ATT3	0x4002727C	FULL	Master attributes 3

21.443 PPU_FX 426

Register Name	Address	Permission	Description
PERI_MS_PPU_FX426_SL_ADDR	0x40027280	FULL	Slave region, base address
PERI_MS_PPU_FX426_SL_SIZE	0x40027284	FULL	Slave region, size
PERI_MS_PPU_FX426_SL_ATT0	0x40027290	FULL	Slave attributes 0
PERI_MS_PPU_FX426_SL_ATT1	0x40027294	FULL	Slave attributes 1
PERI_MS_PPU_FX426_SL_ATT2	0x40027298	FULL	Slave attributes 2
PERI_MS_PPU_FX426_SL_ATT3	0x4002729C	FULL	Slave attributes 3
PERI_MS_PPU_FX426_MS_ADDR	0x400272A0	FULL	Master region, base address
PERI_MS_PPU_FX426_MS_SIZE	0x400272A4	FULL	Master region, size
PERI_MS_PPU_FX426_MS_ATT0	0x400272B0	FULL	Master attributes 0
PERI_MS_PPU_FX426_MS_ATT1	0x400272B4	FULL	Master attributes 1
PERI_MS_PPU_FX426_MS_ATT2	0x400272B8	FULL	Master attributes 2
PERI_MS_PPU_FX426_MS_ATT3	0x400272BC	FULL	Master attributes 3

21.444 PPU_FX 427

Register Name	Address	Permission	Description
PERI_MS_PPU_FX427_SL_ADDR	0x400272C0	FULL	Slave region, base address
PERI_MS_PPU_FX427_SL_SIZE	0x400272C4	FULL	Slave region, size
PERI_MS_PPU_FX427_SL_ATT0	0x400272D0	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX427_SL_ATT1	0x400272D4	FULL	Slave attributes 1
PERI_MS_PPU_FX427_SL_ATT2	0x400272D8	FULL	Slave attributes 2
PERI_MS_PPU_FX427_SL_ATT3	0x400272DC	FULL	Slave attributes 3
PERI_MS_PPU_FX427_MS_ADDR	0x400272E0	FULL	Master region, base address
PERI_MS_PPU_FX427_MS_SIZE	0x400272E4	FULL	Master region, size
PERI_MS_PPU_FX427_MS_ATT0	0x400272F0	FULL	Master attributes 0
PERI_MS_PPU_FX427_MS_ATT1	0x400272F4	FULL	Master attributes 1
PERI_MS_PPU_FX427_MS_ATT2	0x400272F8	FULL	Master attributes 2
PERI_MS_PPU_FX427_MS_ATT3	0x400272FC	FULL	Master attributes 3

21.445 PPU_FX 428

Register Name	Address	Permission	Description
PERI_MS_PPU_FX428_SL_ADDR	0x40027300	FULL	Slave region, base address
PERI_MS_PPU_FX428_SL_SIZE	0x40027304	FULL	Slave region, size
PERI_MS_PPU_FX428_SL_ATT0	0x40027310	FULL	Slave attributes 0
PERI_MS_PPU_FX428_SL_ATT1	0x40027314	FULL	Slave attributes 1
PERI_MS_PPU_FX428_SL_ATT2	0x40027318	FULL	Slave attributes 2
PERI_MS_PPU_FX428_SL_ATT3	0x4002731C	FULL	Slave attributes 3
PERI_MS_PPU_FX428_MS_ADDR	0x40027320	FULL	Master region, base address
PERI_MS_PPU_FX428_MS_SIZE	0x40027324	FULL	Master region, size
PERI_MS_PPU_FX428_MS_ATT0	0x40027330	FULL	Master attributes 0
PERI_MS_PPU_FX428_MS_ATT1	0x40027334	FULL	Master attributes 1
PERI_MS_PPU_FX428_MS_ATT2	0x40027338	FULL	Master attributes 2
PERI_MS_PPU_FX428_MS_ATT3	0x4002733C	FULL	Master attributes 3

21.446 PPU_FX 429

Register Name	Address	Permission	Description
PERI_MS_PPU_FX429_SL_ADDR	0x40027340	FULL	Slave region, base address
PERI_MS_PPU_FX429_SL_SIZE	0x40027344	FULL	Slave region, size
PERI_MS_PPU_FX429_SL_ATT0	0x40027350	FULL	Slave attributes 0
PERI_MS_PPU_FX429_SL_ATT1	0x40027354	FULL	Slave attributes 1
PERI_MS_PPU_FX429_SL_ATT2	0x40027358	FULL	Slave attributes 2
PERI_MS_PPU_FX429_SL_ATT3	0x4002735C	FULL	Slave attributes 3
PERI_MS_PPU_FX429_MS_ADDR	0x40027360	FULL	Master region, base address
PERI_MS_PPU_FX429_MS_SIZE	0x40027364	FULL	Master region, size
PERI_MS_PPU_FX429_MS_ATT0	0x40027370	FULL	Master attributes 0
PERI_MS_PPU_FX429_MS_ATT1	0x40027374	FULL	Master attributes 1
PERI_MS_PPU_FX429_MS_ATT2	0x40027378	FULL	Master attributes 2
PERI_MS_PPU_FX429_MS_ATT3	0x4002737C	FULL	Master attributes 3

21.447 PPU_FX 430

Register Name	Address	Permission	Description
PERI_MS_PPU_FX430_SL_ADDR	0x40027380	FULL	Slave region, base address
PERI_MS_PPU_FX430_SL_SIZE	0x40027384	FULL	Slave region, size
PERI_MS_PPU_FX430_SL_ATT0	0x40027390	FULL	Slave attributes 0
PERI_MS_PPU_FX430_SL_ATT1	0x40027394	FULL	Slave attributes 1
PERI_MS_PPU_FX430_SL_ATT2	0x40027398	FULL	Slave attributes 2
PERI_MS_PPU_FX430_SL_ATT3	0x4002739C	FULL	Slave attributes 3
PERI_MS_PPU_FX430_MS_ADDR	0x400273A0	FULL	Master region, base address
PERI_MS_PPU_FX430_MS_SIZE	0x400273A4	FULL	Master region, size
PERI_MS_PPU_FX430_MS_ATT0	0x400273B0	FULL	Master attributes 0
PERI_MS_PPU_FX430_MS_ATT1	0x400273B4	FULL	Master attributes 1
PERI_MS_PPU_FX430_MS_ATT2	0x400273B8	FULL	Master attributes 2
PERI_MS_PPU_FX430_MS_ATT3	0x400273BC	FULL	Master attributes 3

21.448 PPU_FX 431

Register Name	Address	Permission	Description
PERI_MS_PPU_FX431_SL_ADDR	0x400273C0	FULL	Slave region, base address
PERI_MS_PPU_FX431_SL_SIZE	0x400273C4	FULL	Slave region, size
PERI_MS_PPU_FX431_SL_ATT0	0x400273D0	FULL	Slave attributes 0
PERI_MS_PPU_FX431_SL_ATT1	0x400273D4	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX431_SL_ATT2	0x400273D8	FULL	Slave attributes 2
PERI_MS_PPU_FX431_SL_ATT3	0x400273DC	FULL	Slave attributes 3
PERI_MS_PPU_FX431_MS_ADDR	0x400273E0	FULL	Master region, base address
PERI_MS_PPU_FX431_MS_SIZE	0x400273E4	FULL	Master region, size
PERI_MS_PPU_FX431_MS_ATT0	0x400273F0	FULL	Master attributes 0
PERI_MS_PPU_FX431_MS_ATT1	0x400273F4	FULL	Master attributes 1
PERI_MS_PPU_FX431_MS_ATT2	0x400273F8	FULL	Master attributes 2
PERI_MS_PPU_FX431_MS_ATT3	0x400273FC	FULL	Master attributes 3

21.449 PPU_FX 432

Register Name	Address	Permission	Description
PERI_MS_PPU_FX432_SL_ADDR	0x40027400	FULL	Slave region, base address
PERI_MS_PPU_FX432_SL_SIZE	0x40027404	FULL	Slave region, size
PERI_MS_PPU_FX432_SL_ATT0	0x40027410	FULL	Slave attributes 0
PERI_MS_PPU_FX432_SL_ATT1	0x40027414	FULL	Slave attributes 1
PERI_MS_PPU_FX432_SL_ATT2	0x40027418	FULL	Slave attributes 2
PERI_MS_PPU_FX432_SL_ATT3	0x4002741C	FULL	Slave attributes 3
PERI_MS_PPU_FX432_MS_ADDR	0x40027420	FULL	Master region, base address
PERI_MS_PPU_FX432_MS_SIZE	0x40027424	FULL	Master region, size
PERI_MS_PPU_FX432_MS_ATT0	0x40027430	FULL	Master attributes 0
PERI_MS_PPU_FX432_MS_ATT1	0x40027434	FULL	Master attributes 1
PERI_MS_PPU_FX432_MS_ATT2	0x40027438	FULL	Master attributes 2
PERI_MS_PPU_FX432_MS_ATT3	0x4002743C	FULL	Master attributes 3

21.450 PPU_FX 433

Register Name	Address	Permission	Description
PERI_MS_PPU_FX433_SL_ADDR	0x40027440	FULL	Slave region, base address
PERI_MS_PPU_FX433_SL_SIZE	0x40027444	FULL	Slave region, size
PERI_MS_PPU_FX433_SL_ATT0	0x40027450	FULL	Slave attributes 0
PERI_MS_PPU_FX433_SL_ATT1	0x40027454	FULL	Slave attributes 1
PERI_MS_PPU_FX433_SL_ATT2	0x40027458	FULL	Slave attributes 2
PERI_MS_PPU_FX433_SL_ATT3	0x4002745C	FULL	Slave attributes 3
PERI_MS_PPU_FX433_MS_ADDR	0x40027460	FULL	Master region, base address
PERI_MS_PPU_FX433_MS_SIZE	0x40027464	FULL	Master region, size
PERI_MS_PPU_FX433_MS_ATT0	0x40027470	FULL	Master attributes 0
PERI_MS_PPU_FX433_MS_ATT1	0x40027474	FULL	Master attributes 1
PERI_MS_PPU_FX433_MS_ATT2	0x40027478	FULL	Master attributes 2
PERI_MS_PPU_FX433_MS_ATT3	0x4002747C	FULL	Master attributes 3

21.451 PPU_FX 434

Register Name	Address	Permission	Description
PERI_MS_PPU_FX434_SL_ADDR	0x40027480	FULL	Slave region, base address
PERI_MS_PPU_FX434_SL_SIZE	0x40027484	FULL	Slave region, size
PERI_MS_PPU_FX434_SL_ATT0	0x40027490	FULL	Slave attributes 0
PERI_MS_PPU_FX434_SL_ATT1	0x40027494	FULL	Slave attributes 1
PERI_MS_PPU_FX434_SL_ATT2	0x40027498	FULL	Slave attributes 2
PERI_MS_PPU_FX434_SL_ATT3	0x4002749C	FULL	Slave attributes 3
PERI_MS_PPU_FX434_MS_ADDR	0x400274A0	FULL	Master region, base address
PERI_MS_PPU_FX434_MS_SIZE	0x400274A4	FULL	Master region, size
PERI_MS_PPU_FX434_MS_ATT0	0x400274B0	FULL	Master attributes 0
PERI_MS_PPU_FX434_MS_ATT1	0x400274B4	FULL	Master attributes 1
PERI_MS_PPU_FX434_MS_ATT2	0x400274B8	FULL	Master attributes 2
PERI_MS_PPU_FX434_MS_ATT3	0x400274BC	FULL	Master attributes 3

21.452 PPU_FX 435

Register Name	Address	Permission	Description
PERI_MS_PPU_FX435_SL_ADDR	0x400274C0	FULL	Slave region, base address
PERI_MS_PPU_FX435_SL_SIZE	0x400274C4	FULL	Slave region, size
PERI_MS_PPU_FX435_SL_ATT0	0x400274D0	FULL	Slave attributes 0
PERI_MS_PPU_FX435_SL_ATT1	0x400274D4	FULL	Slave attributes 1
PERI_MS_PPU_FX435_SL_ATT2	0x400274D8	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX435_SL_ATT3	0x400274DC	FULL	Slave attributes 3
PERI_MS_PPU_FX435_MS_ADDR	0x400274E0	FULL	Master region, base address
PERI_MS_PPU_FX435_MS_SIZE	0x400274E4	FULL	Master region, size
PERI_MS_PPU_FX435_MS_ATT0	0x400274F0	FULL	Master attributes 0
PERI_MS_PPU_FX435_MS_ATT1	0x400274F4	FULL	Master attributes 1
PERI_MS_PPU_FX435_MS_ATT2	0x400274F8	FULL	Master attributes 2
PERI_MS_PPU_FX435_MS_ATT3	0x400274FC	FULL	Master attributes 3

21.453 PPU_FX 436

Register Name	Address	Permission	Description
PERI_MS_PPU_FX436_SL_ADDR	0x40027500	FULL	Slave region, base address
PERI_MS_PPU_FX436_SL_SIZE	0x40027504	FULL	Slave region, size
PERI_MS_PPU_FX436_SL_ATT0	0x40027510	FULL	Slave attributes 0
PERI_MS_PPU_FX436_SL_ATT1	0x40027514	FULL	Slave attributes 1
PERI_MS_PPU_FX436_SL_ATT2	0x40027518	FULL	Slave attributes 2
PERI_MS_PPU_FX436_SL_ATT3	0x4002751C	FULL	Slave attributes 3
PERI_MS_PPU_FX436_MS_ADDR	0x40027520	FULL	Master region, base address
PERI_MS_PPU_FX436_MS_SIZE	0x40027524	FULL	Master region, size
PERI_MS_PPU_FX436_MS_ATT0	0x40027530	FULL	Master attributes 0
PERI_MS_PPU_FX436_MS_ATT1	0x40027534	FULL	Master attributes 1
PERI_MS_PPU_FX436_MS_ATT2	0x40027538	FULL	Master attributes 2
PERI_MS_PPU_FX436_MS_ATT3	0x4002753C	FULL	Master attributes 3

21.454 PPU_FX 437

Register Name	Address	Permission	Description
PERI_MS_PPU_FX437_SL_ADDR	0x40027540	FULL	Slave region, base address
PERI_MS_PPU_FX437_SL_SIZE	0x40027544	FULL	Slave region, size
PERI_MS_PPU_FX437_SL_ATT0	0x40027550	FULL	Slave attributes 0
PERI_MS_PPU_FX437_SL_ATT1	0x40027554	FULL	Slave attributes 1
PERI_MS_PPU_FX437_SL_ATT2	0x40027558	FULL	Slave attributes 2
PERI_MS_PPU_FX437_SL_ATT3	0x4002755C	FULL	Slave attributes 3
PERI_MS_PPU_FX437_MS_ADDR	0x40027560	FULL	Master region, base address
PERI_MS_PPU_FX437_MS_SIZE	0x40027564	FULL	Master region, size
PERI_MS_PPU_FX437_MS_ATT0	0x40027570	FULL	Master attributes 0
PERI_MS_PPU_FX437_MS_ATT1	0x40027574	FULL	Master attributes 1
PERI_MS_PPU_FX437_MS_ATT2	0x40027578	FULL	Master attributes 2
PERI_MS_PPU_FX437_MS_ATT3	0x4002757C	FULL	Master attributes 3

21.455 PPU_FX 438

Register Name	Address	Permission	Description
PERI_MS_PPU_FX438_SL_ADDR	0x40027580	FULL	Slave region, base address
PERI_MS_PPU_FX438_SL_SIZE	0x40027584	FULL	Slave region, size
PERI_MS_PPU_FX438_SL_ATT0	0x40027590	FULL	Slave attributes 0
PERI_MS_PPU_FX438_SL_ATT1	0x40027594	FULL	Slave attributes 1
PERI_MS_PPU_FX438_SL_ATT2	0x40027598	FULL	Slave attributes 2
PERI_MS_PPU_FX438_SL_ATT3	0x4002759C	FULL	Slave attributes 3
PERI_MS_PPU_FX438_MS_ADDR	0x400275A0	FULL	Master region, base address
PERI_MS_PPU_FX438_MS_SIZE	0x400275A4	FULL	Master region, size
PERI_MS_PPU_FX438_MS_ATT0	0x400275B0	FULL	Master attributes 0
PERI_MS_PPU_FX438_MS_ATT1	0x400275B4	FULL	Master attributes 1
PERI_MS_PPU_FX438_MS_ATT2	0x400275B8	FULL	Master attributes 2
PERI_MS_PPU_FX438_MS_ATT3	0x400275BC	FULL	Master attributes 3

21.456 PPU_FX 439

Register Name	Address	Permission	Description
PERI_MS_PPU_FX439_SL_ADDR	0x400275C0	FULL	Slave region, base address
PERI_MS_PPU_FX439_SL_SIZE	0x400275C4	FULL	Slave region, size
PERI_MS_PPU_FX439_SL_ATT0	0x400275D0	FULL	Slave attributes 0
PERI_MS_PPU_FX439_SL_ATT1	0x400275D4	FULL	Slave attributes 1
PERI_MS_PPU_FX439_SL_ATT2	0x400275D8	FULL	Slave attributes 2
PERI_MS_PPU_FX439_SL_ATT3	0x400275DC	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX439_MS_ADDR	0x400275E0	FULL	Master region, base address
PERI_MS_PPU_FX439_MS_SIZE	0x400275E4	FULL	Master region, size
PERI_MS_PPU_FX439_MS_ATT0	0x400275F0	FULL	Master attributes 0
PERI_MS_PPU_FX439_MS_ATT1	0x400275F4	FULL	Master attributes 1
PERI_MS_PPU_FX439_MS_ATT2	0x400275F8	FULL	Master attributes 2
PERI_MS_PPU_FX439_MS_ATT3	0x400275FC	FULL	Master attributes 3

21.457 PPU_FX 440

Register Name	Address	Permission	Description
PERI_MS_PPU_FX440_SL_ADDR	0x40027600	FULL	Slave region, base address
PERI_MS_PPU_FX440_SL_SIZE	0x40027604	FULL	Slave region, size
PERI_MS_PPU_FX440_SL_ATT0	0x40027610	FULL	Slave attributes 0
PERI_MS_PPU_FX440_SL_ATT1	0x40027614	FULL	Slave attributes 1
PERI_MS_PPU_FX440_SL_ATT2	0x40027618	FULL	Slave attributes 2
PERI_MS_PPU_FX440_SL_ATT3	0x4002761C	FULL	Slave attributes 3
PERI_MS_PPU_FX440_MS_ADDR	0x40027620	FULL	Master region, base address
PERI_MS_PPU_FX440_MS_SIZE	0x40027624	FULL	Master region, size
PERI_MS_PPU_FX440_MS_ATT0	0x40027630	FULL	Master attributes 0
PERI_MS_PPU_FX440_MS_ATT1	0x40027634	FULL	Master attributes 1
PERI_MS_PPU_FX440_MS_ATT2	0x40027638	FULL	Master attributes 2
PERI_MS_PPU_FX440_MS_ATT3	0x4002763C	FULL	Master attributes 3

21.458 PPU_FX 441

Register Name	Address	Permission	Description
PERI_MS_PPU_FX441_SL_ADDR	0x40027640	FULL	Slave region, base address
PERI_MS_PPU_FX441_SL_SIZE	0x40027644	FULL	Slave region, size
PERI_MS_PPU_FX441_SL_ATT0	0x40027650	FULL	Slave attributes 0
PERI_MS_PPU_FX441_SL_ATT1	0x40027654	FULL	Slave attributes 1
PERI_MS_PPU_FX441_SL_ATT2	0x40027658	FULL	Slave attributes 2
PERI_MS_PPU_FX441_SL_ATT3	0x4002765C	FULL	Slave attributes 3
PERI_MS_PPU_FX441_MS_ADDR	0x40027660	FULL	Master region, base address
PERI_MS_PPU_FX441_MS_SIZE	0x40027664	FULL	Master region, size
PERI_MS_PPU_FX441_MS_ATT0	0x40027670	FULL	Master attributes 0
PERI_MS_PPU_FX441_MS_ATT1	0x40027674	FULL	Master attributes 1
PERI_MS_PPU_FX441_MS_ATT2	0x40027678	FULL	Master attributes 2
PERI_MS_PPU_FX441_MS_ATT3	0x4002767C	FULL	Master attributes 3

21.459 PPU_FX 442

Register Name	Address	Permission	Description
PERI_MS_PPU_FX442_SL_ADDR	0x40027680	FULL	Slave region, base address
PERI_MS_PPU_FX442_SL_SIZE	0x40027684	FULL	Slave region, size
PERI_MS_PPU_FX442_SL_ATT0	0x40027690	FULL	Slave attributes 0
PERI_MS_PPU_FX442_SL_ATT1	0x40027694	FULL	Slave attributes 1
PERI_MS_PPU_FX442_SL_ATT2	0x40027698	FULL	Slave attributes 2
PERI_MS_PPU_FX442_SL_ATT3	0x4002769C	FULL	Slave attributes 3
PERI_MS_PPU_FX442_MS_ADDR	0x400276A0	FULL	Master region, base address
PERI_MS_PPU_FX442_MS_SIZE	0x400276A4	FULL	Master region, size
PERI_MS_PPU_FX442_MS_ATT0	0x400276B0	FULL	Master attributes 0
PERI_MS_PPU_FX442_MS_ATT1	0x400276B4	FULL	Master attributes 1
PERI_MS_PPU_FX442_MS_ATT2	0x400276B8	FULL	Master attributes 2
PERI_MS_PPU_FX442_MS_ATT3	0x400276BC	FULL	Master attributes 3

21.460 PPU_FX 443

Register Name	Address	Permission	Description
PERI_MS_PPU_FX443_SL_ADDR	0x400276C0	FULL	Slave region, base address
PERI_MS_PPU_FX443_SL_SIZE	0x400276C4	FULL	Slave region, size
PERI_MS_PPU_FX443_SL_ATT0	0x400276D0	FULL	Slave attributes 0
PERI_MS_PPU_FX443_SL_ATT1	0x400276D4	FULL	Slave attributes 1
PERI_MS_PPU_FX443_SL_ATT2	0x400276D8	FULL	Slave attributes 2
PERI_MS_PPU_FX443_SL_ATT3	0x400276DC	FULL	Slave attributes 3
PERI_MS_PPU_FX443_MS_ADDR	0x400276E0	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX443_MS_SIZE	0x400276E4	FULL	Master region, size
PERI_MS_PPU_FX443_MS_ATT0	0x400276F0	FULL	Master attributes 0
PERI_MS_PPU_FX443_MS_ATT1	0x400276F4	FULL	Master attributes 1
PERI_MS_PPU_FX443_MS_ATT2	0x400276F8	FULL	Master attributes 2
PERI_MS_PPU_FX443_MS_ATT3	0x400276FC	FULL	Master attributes 3

21.461 PPU_FX 444

Register Name	Address	Permission	Description
PERI_MS_PPU_FX444_SL_ADDR	0x40027700	FULL	Slave region, base address
PERI_MS_PPU_FX444_SL_SIZE	0x40027704	FULL	Slave region, size
PERI_MS_PPU_FX444_SL_ATT0	0x40027710	FULL	Slave attributes 0
PERI_MS_PPU_FX444_SL_ATT1	0x40027714	FULL	Slave attributes 1
PERI_MS_PPU_FX444_SL_ATT2	0x40027718	FULL	Slave attributes 2
PERI_MS_PPU_FX444_SL_ATT3	0x4002771C	FULL	Slave attributes 3
PERI_MS_PPU_FX444_MS_ADDR	0x40027720	FULL	Master region, base address
PERI_MS_PPU_FX444_MS_SIZE	0x40027724	FULL	Master region, size
PERI_MS_PPU_FX444_MS_ATT0	0x40027730	FULL	Master attributes 0
PERI_MS_PPU_FX444_MS_ATT1	0x40027734	FULL	Master attributes 1
PERI_MS_PPU_FX444_MS_ATT2	0x40027738	FULL	Master attributes 2
PERI_MS_PPU_FX444_MS_ATT3	0x4002773C	FULL	Master attributes 3

21.462 PPU_FX 445

Register Name	Address	Permission	Description
PERI_MS_PPU_FX445_SL_ADDR	0x40027740	FULL	Slave region, base address
PERI_MS_PPU_FX445_SL_SIZE	0x40027744	FULL	Slave region, size
PERI_MS_PPU_FX445_SL_ATT0	0x40027750	FULL	Slave attributes 0
PERI_MS_PPU_FX445_SL_ATT1	0x40027754	FULL	Slave attributes 1
PERI_MS_PPU_FX445_SL_ATT2	0x40027758	FULL	Slave attributes 2
PERI_MS_PPU_FX445_SL_ATT3	0x4002775C	FULL	Slave attributes 3
PERI_MS_PPU_FX445_MS_ADDR	0x40027760	FULL	Master region, base address
PERI_MS_PPU_FX445_MS_SIZE	0x40027764	FULL	Master region, size
PERI_MS_PPU_FX445_MS_ATT0	0x40027770	FULL	Master attributes 0
PERI_MS_PPU_FX445_MS_ATT1	0x40027774	FULL	Master attributes 1
PERI_MS_PPU_FX445_MS_ATT2	0x40027778	FULL	Master attributes 2
PERI_MS_PPU_FX445_MS_ATT3	0x4002777C	FULL	Master attributes 3

21.463 PPU_FX 446

Register Name	Address	Permission	Description
PERI_MS_PPU_FX446_SL_ADDR	0x40027780	FULL	Slave region, base address
PERI_MS_PPU_FX446_SL_SIZE	0x40027784	FULL	Slave region, size
PERI_MS_PPU_FX446_SL_ATT0	0x40027790	FULL	Slave attributes 0
PERI_MS_PPU_FX446_SL_ATT1	0x40027794	FULL	Slave attributes 1
PERI_MS_PPU_FX446_SL_ATT2	0x40027798	FULL	Slave attributes 2
PERI_MS_PPU_FX446_SL_ATT3	0x4002779C	FULL	Slave attributes 3
PERI_MS_PPU_FX446_MS_ADDR	0x400277A0	FULL	Master region, base address
PERI_MS_PPU_FX446_MS_SIZE	0x400277A4	FULL	Master region, size
PERI_MS_PPU_FX446_MS_ATT0	0x400277B0	FULL	Master attributes 0
PERI_MS_PPU_FX446_MS_ATT1	0x400277B4	FULL	Master attributes 1
PERI_MS_PPU_FX446_MS_ATT2	0x400277B8	FULL	Master attributes 2
PERI_MS_PPU_FX446_MS_ATT3	0x400277BC	FULL	Master attributes 3

21.464 PPU_FX 447

Register Name	Address	Permission	Description
PERI_MS_PPU_FX447_SL_ADDR	0x400277C0	FULL	Slave region, base address
PERI_MS_PPU_FX447_SL_SIZE	0x400277C4	FULL	Slave region, size
PERI_MS_PPU_FX447_SL_ATT0	0x400277D0	FULL	Slave attributes 0
PERI_MS_PPU_FX447_SL_ATT1	0x400277D4	FULL	Slave attributes 1
PERI_MS_PPU_FX447_SL_ATT2	0x400277D8	FULL	Slave attributes 2
PERI_MS_PPU_FX447_SL_ATT3	0x400277DC	FULL	Slave attributes 3
PERI_MS_PPU_FX447_MS_ADDR	0x400277E0	FULL	Master region, base address
PERI_MS_PPU_FX447_MS_SIZE	0x400277E4	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX447_MS_ATT0	0x400277F0	FULL	Master attributes 0
PERI_MS_PPU_FX447_MS_ATT1	0x400277F4	FULL	Master attributes 1
PERI_MS_PPU_FX447_MS_ATT2	0x400277F8	FULL	Master attributes 2
PERI_MS_PPU_FX447_MS_ATT3	0x400277FC	FULL	Master attributes 3

21.465 PPU_FX 448

Register Name	Address	Permission	Description
PERI_MS_PPU_FX448_SL_ADDR	0x40027800	FULL	Slave region, base address
PERI_MS_PPU_FX448_SL_SIZE	0x40027804	FULL	Slave region, size
PERI_MS_PPU_FX448_SL_ATT0	0x40027810	FULL	Slave attributes 0
PERI_MS_PPU_FX448_SL_ATT1	0x40027814	FULL	Slave attributes 1
PERI_MS_PPU_FX448_SL_ATT2	0x40027818	FULL	Slave attributes 2
PERI_MS_PPU_FX448_SL_ATT3	0x4002781C	FULL	Slave attributes 3
PERI_MS_PPU_FX448_MS_ADDR	0x40027820	FULL	Master region, base address
PERI_MS_PPU_FX448_MS_SIZE	0x40027824	FULL	Master region, size
PERI_MS_PPU_FX448_MS_ATT0	0x40027830	FULL	Master attributes 0
PERI_MS_PPU_FX448_MS_ATT1	0x40027834	FULL	Master attributes 1
PERI_MS_PPU_FX448_MS_ATT2	0x40027838	FULL	Master attributes 2
PERI_MS_PPU_FX448_MS_ATT3	0x4002783C	FULL	Master attributes 3

21.466 PPU_FX 449

Register Name	Address	Permission	Description
PERI_MS_PPU_FX449_SL_ADDR	0x40027840	FULL	Slave region, base address
PERI_MS_PPU_FX449_SL_SIZE	0x40027844	FULL	Slave region, size
PERI_MS_PPU_FX449_SL_ATT0	0x40027850	FULL	Slave attributes 0
PERI_MS_PPU_FX449_SL_ATT1	0x40027854	FULL	Slave attributes 1
PERI_MS_PPU_FX449_SL_ATT2	0x40027858	FULL	Slave attributes 2
PERI_MS_PPU_FX449_SL_ATT3	0x4002785C	FULL	Slave attributes 3
PERI_MS_PPU_FX449_MS_ADDR	0x40027860	FULL	Master region, base address
PERI_MS_PPU_FX449_MS_SIZE	0x40027864	FULL	Master region, size
PERI_MS_PPU_FX449_MS_ATT0	0x40027870	FULL	Master attributes 0
PERI_MS_PPU_FX449_MS_ATT1	0x40027874	FULL	Master attributes 1
PERI_MS_PPU_FX449_MS_ATT2	0x40027878	FULL	Master attributes 2
PERI_MS_PPU_FX449_MS_ATT3	0x4002787C	FULL	Master attributes 3

21.467 PPU_FX 450

Register Name	Address	Permission	Description
PERI_MS_PPU_FX450_SL_ADDR	0x40027880	FULL	Slave region, base address
PERI_MS_PPU_FX450_SL_SIZE	0x40027884	FULL	Slave region, size
PERI_MS_PPU_FX450_SL_ATT0	0x40027890	FULL	Slave attributes 0
PERI_MS_PPU_FX450_SL_ATT1	0x40027894	FULL	Slave attributes 1
PERI_MS_PPU_FX450_SL_ATT2	0x40027898	FULL	Slave attributes 2
PERI_MS_PPU_FX450_SL_ATT3	0x4002789C	FULL	Slave attributes 3
PERI_MS_PPU_FX450_MS_ADDR	0x400278A0	FULL	Master region, base address
PERI_MS_PPU_FX450_MS_SIZE	0x400278A4	FULL	Master region, size
PERI_MS_PPU_FX450_MS_ATT0	0x400278B0	FULL	Master attributes 0
PERI_MS_PPU_FX450_MS_ATT1	0x400278B4	FULL	Master attributes 1
PERI_MS_PPU_FX450_MS_ATT2	0x400278B8	FULL	Master attributes 2
PERI_MS_PPU_FX450_MS_ATT3	0x400278BC	FULL	Master attributes 3

21.468 PPU_FX 451

Register Name	Address	Permission	Description
PERI_MS_PPU_FX451_SL_ADDR	0x400278C0	FULL	Slave region, base address
PERI_MS_PPU_FX451_SL_SIZE	0x400278C4	FULL	Slave region, size
PERI_MS_PPU_FX451_SL_ATT0	0x400278D0	FULL	Slave attributes 0
PERI_MS_PPU_FX451_SL_ATT1	0x400278D4	FULL	Slave attributes 1
PERI_MS_PPU_FX451_SL_ATT2	0x400278D8	FULL	Slave attributes 2
PERI_MS_PPU_FX451_SL_ATT3	0x400278DC	FULL	Slave attributes 3
PERI_MS_PPU_FX451_MS_ADDR	0x400278E0	FULL	Master region, base address
PERI_MS_PPU_FX451_MS_SIZE	0x400278E4	FULL	Master region, size
PERI_MS_PPU_FX451_MS_ATT0	0x400278F0	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX451_MS_ATT1	0x400278F4	FULL	Master attributes 1
PERI_MS_PPU_FX451_MS_ATT2	0x400278F8	FULL	Master attributes 2
PERI_MS_PPU_FX451_MS_ATT3	0x400278FC	FULL	Master attributes 3

21.469 PPU_FX 452

Register Name	Address	Permission	Description
PERI_MS_PPU_FX452_SL_ADDR	0x40027900	FULL	Slave region, base address
PERI_MS_PPU_FX452_SL_SIZE	0x40027904	FULL	Slave region, size
PERI_MS_PPU_FX452_SL_ATT0	0x40027910	FULL	Slave attributes 0
PERI_MS_PPU_FX452_SL_ATT1	0x40027914	FULL	Slave attributes 1
PERI_MS_PPU_FX452_SL_ATT2	0x40027918	FULL	Slave attributes 2
PERI_MS_PPU_FX452_SL_ATT3	0x4002791C	FULL	Slave attributes 3
PERI_MS_PPU_FX452_MS_ADDR	0x40027920	FULL	Master region, base address
PERI_MS_PPU_FX452_MS_SIZE	0x40027924	FULL	Master region, size
PERI_MS_PPU_FX452_MS_ATT0	0x40027930	FULL	Master attributes 0
PERI_MS_PPU_FX452_MS_ATT1	0x40027934	FULL	Master attributes 1
PERI_MS_PPU_FX452_MS_ATT2	0x40027938	FULL	Master attributes 2
PERI_MS_PPU_FX452_MS_ATT3	0x4002793C	FULL	Master attributes 3

21.470 PPU_FX 453

Register Name	Address	Permission	Description
PERI_MS_PPU_FX453_SL_ADDR	0x40027940	FULL	Slave region, base address
PERI_MS_PPU_FX453_SL_SIZE	0x40027944	FULL	Slave region, size
PERI_MS_PPU_FX453_SL_ATT0	0x40027950	FULL	Slave attributes 0
PERI_MS_PPU_FX453_SL_ATT1	0x40027954	FULL	Slave attributes 1
PERI_MS_PPU_FX453_SL_ATT2	0x40027958	FULL	Slave attributes 2
PERI_MS_PPU_FX453_SL_ATT3	0x4002795C	FULL	Slave attributes 3
PERI_MS_PPU_FX453_MS_ADDR	0x40027960	FULL	Master region, base address
PERI_MS_PPU_FX453_MS_SIZE	0x40027964	FULL	Master region, size
PERI_MS_PPU_FX453_MS_ATT0	0x40027970	FULL	Master attributes 0
PERI_MS_PPU_FX453_MS_ATT1	0x40027974	FULL	Master attributes 1
PERI_MS_PPU_FX453_MS_ATT2	0x40027978	FULL	Master attributes 2
PERI_MS_PPU_FX453_MS_ATT3	0x4002797C	FULL	Master attributes 3

21.471 PPU_FX 454

Register Name	Address	Permission	Description
PERI_MS_PPU_FX454_SL_ADDR	0x40027980	FULL	Slave region, base address
PERI_MS_PPU_FX454_SL_SIZE	0x40027984	FULL	Slave region, size
PERI_MS_PPU_FX454_SL_ATT0	0x40027990	FULL	Slave attributes 0
PERI_MS_PPU_FX454_SL_ATT1	0x40027994	FULL	Slave attributes 1
PERI_MS_PPU_FX454_SL_ATT2	0x40027998	FULL	Slave attributes 2
PERI_MS_PPU_FX454_SL_ATT3	0x4002799C	FULL	Slave attributes 3
PERI_MS_PPU_FX454_MS_ADDR	0x400279A0	FULL	Master region, base address
PERI_MS_PPU_FX454_MS_SIZE	0x400279A4	FULL	Master region, size
PERI_MS_PPU_FX454_MS_ATT0	0x400279B0	FULL	Master attributes 0
PERI_MS_PPU_FX454_MS_ATT1	0x400279B4	FULL	Master attributes 1
PERI_MS_PPU_FX454_MS_ATT2	0x400279B8	FULL	Master attributes 2
PERI_MS_PPU_FX454_MS_ATT3	0x400279BC	FULL	Master attributes 3

21.472 PPU_FX 455

Register Name	Address	Permission	Description
PERI_MS_PPU_FX455_SL_ADDR	0x400279C0	FULL	Slave region, base address
PERI_MS_PPU_FX455_SL_SIZE	0x400279C4	FULL	Slave region, size
PERI_MS_PPU_FX455_SL_ATT0	0x400279D0	FULL	Slave attributes 0
PERI_MS_PPU_FX455_SL_ATT1	0x400279D4	FULL	Slave attributes 1
PERI_MS_PPU_FX455_SL_ATT2	0x400279D8	FULL	Slave attributes 2
PERI_MS_PPU_FX455_SL_ATT3	0x400279DC	FULL	Slave attributes 3
PERI_MS_PPU_FX455_MS_ADDR	0x400279E0	FULL	Master region, base address
PERI_MS_PPU_FX455_MS_SIZE	0x400279E4	FULL	Master region, size
PERI_MS_PPU_FX455_MS_ATT0	0x400279F0	FULL	Master attributes 0
PERI_MS_PPU_FX455_MS_ATT1	0x400279F4	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX455_MS_ATT2	0x400279F8	FULL	Master attributes 2
PERI_MS_PPU_FX455_MS_ATT3	0x400279FC	FULL	Master attributes 3

21.473 PPU_FX 456

Register Name	Address	Permission	Description
PERI_MS_PPU_FX456_SL_ADDR	0x40027A00	FULL	Slave region, base address
PERI_MS_PPU_FX456_SL_SIZE	0x40027A04	FULL	Slave region, size
PERI_MS_PPU_FX456_SL_ATT0	0x40027A10	FULL	Slave attributes 0
PERI_MS_PPU_FX456_SL_ATT1	0x40027A14	FULL	Slave attributes 1
PERI_MS_PPU_FX456_SL_ATT2	0x40027A18	FULL	Slave attributes 2
PERI_MS_PPU_FX456_SL_ATT3	0x40027A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX456_MS_ADDR	0x40027A20	FULL	Master region, base address
PERI_MS_PPU_FX456_MS_SIZE	0x40027A24	FULL	Master region, size
PERI_MS_PPU_FX456_MS_ATT0	0x40027A30	FULL	Master attributes 0
PERI_MS_PPU_FX456_MS_ATT1	0x40027A34	FULL	Master attributes 1
PERI_MS_PPU_FX456_MS_ATT2	0x40027A38	FULL	Master attributes 2
PERI_MS_PPU_FX456_MS_ATT3	0x40027A3C	FULL	Master attributes 3

21.474 PPU_FX 457

Register Name	Address	Permission	Description
PERI_MS_PPU_FX457_SL_ADDR	0x40027A40	FULL	Slave region, base address
PERI_MS_PPU_FX457_SL_SIZE	0x40027A44	FULL	Slave region, size
PERI_MS_PPU_FX457_SL_ATT0	0x40027A50	FULL	Slave attributes 0
PERI_MS_PPU_FX457_SL_ATT1	0x40027A54	FULL	Slave attributes 1
PERI_MS_PPU_FX457_SL_ATT2	0x40027A58	FULL	Slave attributes 2
PERI_MS_PPU_FX457_SL_ATT3	0x40027A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX457_MS_ADDR	0x40027A60	FULL	Master region, base address
PERI_MS_PPU_FX457_MS_SIZE	0x40027A64	FULL	Master region, size
PERI_MS_PPU_FX457_MS_ATT0	0x40027A70	FULL	Master attributes 0
PERI_MS_PPU_FX457_MS_ATT1	0x40027A74	FULL	Master attributes 1
PERI_MS_PPU_FX457_MS_ATT2	0x40027A78	FULL	Master attributes 2
PERI_MS_PPU_FX457_MS_ATT3	0x40027A7C	FULL	Master attributes 3

21.475 PPU_FX 458

Register Name	Address	Permission	Description
PERI_MS_PPU_FX458_SL_ADDR	0x40027A80	FULL	Slave region, base address
PERI_MS_PPU_FX458_SL_SIZE	0x40027A84	FULL	Slave region, size
PERI_MS_PPU_FX458_SL_ATT0	0x40027A90	FULL	Slave attributes 0
PERI_MS_PPU_FX458_SL_ATT1	0x40027A94	FULL	Slave attributes 1
PERI_MS_PPU_FX458_SL_ATT2	0x40027A98	FULL	Slave attributes 2
PERI_MS_PPU_FX458_SL_ATT3	0x40027A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX458_MS_ADDR	0x40027AA0	FULL	Master region, base address
PERI_MS_PPU_FX458_MS_SIZE	0x40027AA4	FULL	Master region, size
PERI_MS_PPU_FX458_MS_ATT0	0x40027AB0	FULL	Master attributes 0
PERI_MS_PPU_FX458_MS_ATT1	0x40027AB4	FULL	Master attributes 1
PERI_MS_PPU_FX458_MS_ATT2	0x40027AB8	FULL	Master attributes 2
PERI_MS_PPU_FX458_MS_ATT3	0x40027ABC	FULL	Master attributes 3

21.476 PPU_FX 459

Register Name	Address	Permission	Description
PERI_MS_PPU_FX459_SL_ADDR	0x40027AC0	FULL	Slave region, base address
PERI_MS_PPU_FX459_SL_SIZE	0x40027AC4	FULL	Slave region, size
PERI_MS_PPU_FX459_SL_ATT0	0x40027AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX459_SL_ATT1	0x40027AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX459_SL_ATT2	0x40027AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX459_SL_ATT3	0x40027ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX459_MS_ADDR	0x40027AE0	FULL	Master region, base address
PERI_MS_PPU_FX459_MS_SIZE	0x40027AE4	FULL	Master region, size
PERI_MS_PPU_FX459_MS_ATT0	0x40027AF0	FULL	Master attributes 0
PERI_MS_PPU_FX459_MS_ATT1	0x40027AF4	FULL	Master attributes 1
PERI_MS_PPU_FX459_MS_ATT2	0x40027AF8	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX459_MS_ATT3	0x40027AFC	FULL	Master attributes 3

21.477 PPU_FX 460

Register Name	Address	Permission	Description
PERI_MS_PPU_FX460_SL_ADDR	0x40027B00	FULL	Slave region, base address
PERI_MS_PPU_FX460_SL_SIZE	0x40027B04	FULL	Slave region, size
PERI_MS_PPU_FX460_SL_ATT0	0x40027B10	FULL	Slave attributes 0
PERI_MS_PPU_FX460_SL_ATT1	0x40027B14	FULL	Slave attributes 1
PERI_MS_PPU_FX460_SL_ATT2	0x40027B18	FULL	Slave attributes 2
PERI_MS_PPU_FX460_SL_ATT3	0x40027B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX460_MS_ADDR	0x40027B20	FULL	Master region, base address
PERI_MS_PPU_FX460_MS_SIZE	0x40027B24	FULL	Master region, size
PERI_MS_PPU_FX460_MS_ATT0	0x40027B30	FULL	Master attributes 0
PERI_MS_PPU_FX460_MS_ATT1	0x40027B34	FULL	Master attributes 1
PERI_MS_PPU_FX460_MS_ATT2	0x40027B38	FULL	Master attributes 2
PERI_MS_PPU_FX460_MS_ATT3	0x40027B3C	FULL	Master attributes 3

21.478 PPU_FX 461

Register Name	Address	Permission	Description
PERI_MS_PPU_FX461_SL_ADDR	0x40027B40	FULL	Slave region, base address
PERI_MS_PPU_FX461_SL_SIZE	0x40027B44	FULL	Slave region, size
PERI_MS_PPU_FX461_SL_ATT0	0x40027B50	FULL	Slave attributes 0
PERI_MS_PPU_FX461_SL_ATT1	0x40027B54	FULL	Slave attributes 1
PERI_MS_PPU_FX461_SL_ATT2	0x40027B58	FULL	Slave attributes 2
PERI_MS_PPU_FX461_SL_ATT3	0x40027B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX461_MS_ADDR	0x40027B60	FULL	Master region, base address
PERI_MS_PPU_FX461_MS_SIZE	0x40027B64	FULL	Master region, size
PERI_MS_PPU_FX461_MS_ATT0	0x40027B70	FULL	Master attributes 0
PERI_MS_PPU_FX461_MS_ATT1	0x40027B74	FULL	Master attributes 1
PERI_MS_PPU_FX461_MS_ATT2	0x40027B78	FULL	Master attributes 2
PERI_MS_PPU_FX461_MS_ATT3	0x40027B7C	FULL	Master attributes 3

21.479 PPU_FX 462

Register Name	Address	Permission	Description
PERI_MS_PPU_FX462_SL_ADDR	0x40027B80	FULL	Slave region, base address
PERI_MS_PPU_FX462_SL_SIZE	0x40027B84	FULL	Slave region, size
PERI_MS_PPU_FX462_SL_ATT0	0x40027B90	FULL	Slave attributes 0
PERI_MS_PPU_FX462_SL_ATT1	0x40027B94	FULL	Slave attributes 1
PERI_MS_PPU_FX462_SL_ATT2	0x40027B98	FULL	Slave attributes 2
PERI_MS_PPU_FX462_SL_ATT3	0x40027B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX462_MS_ADDR	0x40027BA0	FULL	Master region, base address
PERI_MS_PPU_FX462_MS_SIZE	0x40027BA4	FULL	Master region, size
PERI_MS_PPU_FX462_MS_ATT0	0x40027BB0	FULL	Master attributes 0
PERI_MS_PPU_FX462_MS_ATT1	0x40027BB4	FULL	Master attributes 1
PERI_MS_PPU_FX462_MS_ATT2	0x40027BB8	FULL	Master attributes 2
PERI_MS_PPU_FX462_MS_ATT3	0x40027BBC	FULL	Master attributes 3

21.480 PPU_FX 463

Register Name	Address	Permission	Description
PERI_MS_PPU_FX463_SL_ADDR	0x40027BC0	FULL	Slave region, base address
PERI_MS_PPU_FX463_SL_SIZE	0x40027BC4	FULL	Slave region, size
PERI_MS_PPU_FX463_SL_ATT0	0x40027BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX463_SL_ATT1	0x40027BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX463_SL_ATT2	0x40027BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX463_SL_ATT3	0x40027BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX463_MS_ADDR	0x40027BE0	FULL	Master region, base address
PERI_MS_PPU_FX463_MS_SIZE	0x40027BE4	FULL	Master region, size
PERI_MS_PPU_FX463_MS_ATT0	0x40027BF0	FULL	Master attributes 0
PERI_MS_PPU_FX463_MS_ATT1	0x40027BF4	FULL	Master attributes 1
PERI_MS_PPU_FX463_MS_ATT2	0x40027BF8	FULL	Master attributes 2
PERI_MS_PPU_FX463_MS_ATT3	0x40027BFC	FULL	Master attributes 3

21.481 PPU_FX 464

Register Name	Address	Permission	Description
PERI_MS_PPU_FX464_SL_ADDR	0x40027C00	FULL	Slave region, base address
PERI_MS_PPU_FX464_SL_SIZE	0x40027C04	FULL	Slave region, size
PERI_MS_PPU_FX464_SL_ATT0	0x40027C10	FULL	Slave attributes 0
PERI_MS_PPU_FX464_SL_ATT1	0x40027C14	FULL	Slave attributes 1
PERI_MS_PPU_FX464_SL_ATT2	0x40027C18	FULL	Slave attributes 2
PERI_MS_PPU_FX464_SL_ATT3	0x40027C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX464_MS_ADDR	0x40027C20	FULL	Master region, base address
PERI_MS_PPU_FX464_MS_SIZE	0x40027C24	FULL	Master region, size
PERI_MS_PPU_FX464_MS_ATT0	0x40027C30	FULL	Master attributes 0
PERI_MS_PPU_FX464_MS_ATT1	0x40027C34	FULL	Master attributes 1
PERI_MS_PPU_FX464_MS_ATT2	0x40027C38	FULL	Master attributes 2
PERI_MS_PPU_FX464_MS_ATT3	0x40027C3C	FULL	Master attributes 3

21.482 PPU_FX 465

Register Name	Address	Permission	Description
PERI_MS_PPU_FX465_SL_ADDR	0x40027C40	FULL	Slave region, base address
PERI_MS_PPU_FX465_SL_SIZE	0x40027C44	FULL	Slave region, size
PERI_MS_PPU_FX465_SL_ATT0	0x40027C50	FULL	Slave attributes 0
PERI_MS_PPU_FX465_SL_ATT1	0x40027C54	FULL	Slave attributes 1
PERI_MS_PPU_FX465_SL_ATT2	0x40027C58	FULL	Slave attributes 2
PERI_MS_PPU_FX465_SL_ATT3	0x40027C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX465_MS_ADDR	0x40027C60	FULL	Master region, base address
PERI_MS_PPU_FX465_MS_SIZE	0x40027C64	FULL	Master region, size
PERI_MS_PPU_FX465_MS_ATT0	0x40027C70	FULL	Master attributes 0
PERI_MS_PPU_FX465_MS_ATT1	0x40027C74	FULL	Master attributes 1
PERI_MS_PPU_FX465_MS_ATT2	0x40027C78	FULL	Master attributes 2
PERI_MS_PPU_FX465_MS_ATT3	0x40027C7C	FULL	Master attributes 3

21.483 PPU_FX 466

Register Name	Address	Permission	Description
PERI_MS_PPU_FX466_SL_ADDR	0x40027C80	FULL	Slave region, base address
PERI_MS_PPU_FX466_SL_SIZE	0x40027C84	FULL	Slave region, size
PERI_MS_PPU_FX466_SL_ATT0	0x40027C90	FULL	Slave attributes 0
PERI_MS_PPU_FX466_SL_ATT1	0x40027C94	FULL	Slave attributes 1
PERI_MS_PPU_FX466_SL_ATT2	0x40027C98	FULL	Slave attributes 2
PERI_MS_PPU_FX466_SL_ATT3	0x40027C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX466_MS_ADDR	0x40027CA0	FULL	Master region, base address
PERI_MS_PPU_FX466_MS_SIZE	0x40027CA4	FULL	Master region, size
PERI_MS_PPU_FX466_MS_ATT0	0x40027CB0	FULL	Master attributes 0
PERI_MS_PPU_FX466_MS_ATT1	0x40027CB4	FULL	Master attributes 1
PERI_MS_PPU_FX466_MS_ATT2	0x40027CB8	FULL	Master attributes 2
PERI_MS_PPU_FX466_MS_ATT3	0x40027CBC	FULL	Master attributes 3

21.484 PPU_FX 467

Register Name	Address	Permission	Description
PERI_MS_PPU_FX467_SL_ADDR	0x40027CC0	FULL	Slave region, base address
PERI_MS_PPU_FX467_SL_SIZE	0x40027CC4	FULL	Slave region, size
PERI_MS_PPU_FX467_SL_ATT0	0x40027CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX467_SL_ATT1	0x40027CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX467_SL_ATT2	0x40027CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX467_SL_ATT3	0x40027CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX467_MS_ADDR	0x40027CE0	FULL	Master region, base address
PERI_MS_PPU_FX467_MS_SIZE	0x40027CE4	FULL	Master region, size
PERI_MS_PPU_FX467_MS_ATT0	0x40027CF0	FULL	Master attributes 0
PERI_MS_PPU_FX467_MS_ATT1	0x40027CF4	FULL	Master attributes 1
PERI_MS_PPU_FX467_MS_ATT2	0x40027CF8	FULL	Master attributes 2
PERI_MS_PPU_FX467_MS_ATT3	0x40027CFC	FULL	Master attributes 3

21.485 PPU_FX 468

Register Name	Address	Permission	Description
PERI_MS_PPU_FX468_SL_ADDR	0x40027D00	FULL	Slave region, base address
PERI_MS_PPU_FX468_SL_SIZE	0x40027D04	FULL	Slave region, size
PERI_MS_PPU_FX468_SL_ATT0	0x40027D10	FULL	Slave attributes 0
PERI_MS_PPU_FX468_SL_ATT1	0x40027D14	FULL	Slave attributes 1
PERI_MS_PPU_FX468_SL_ATT2	0x40027D18	FULL	Slave attributes 2
PERI_MS_PPU_FX468_SL_ATT3	0x40027D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX468_MS_ADDR	0x40027D20	FULL	Master region, base address
PERI_MS_PPU_FX468_MS_SIZE	0x40027D24	FULL	Master region, size
PERI_MS_PPU_FX468_MS_ATT0	0x40027D30	FULL	Master attributes 0
PERI_MS_PPU_FX468_MS_ATT1	0x40027D34	FULL	Master attributes 1
PERI_MS_PPU_FX468_MS_ATT2	0x40027D38	FULL	Master attributes 2
PERI_MS_PPU_FX468_MS_ATT3	0x40027D3C	FULL	Master attributes 3

21.486 PPU_FX 469

Register Name	Address	Permission	Description
PERI_MS_PPU_FX469_SL_ADDR	0x40027D40	FULL	Slave region, base address
PERI_MS_PPU_FX469_SL_SIZE	0x40027D44	FULL	Slave region, size
PERI_MS_PPU_FX469_SL_ATT0	0x40027D50	FULL	Slave attributes 0
PERI_MS_PPU_FX469_SL_ATT1	0x40027D54	FULL	Slave attributes 1
PERI_MS_PPU_FX469_SL_ATT2	0x40027D58	FULL	Slave attributes 2
PERI_MS_PPU_FX469_SL_ATT3	0x40027D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX469_MS_ADDR	0x40027D60	FULL	Master region, base address
PERI_MS_PPU_FX469_MS_SIZE	0x40027D64	FULL	Master region, size
PERI_MS_PPU_FX469_MS_ATT0	0x40027D70	FULL	Master attributes 0
PERI_MS_PPU_FX469_MS_ATT1	0x40027D74	FULL	Master attributes 1
PERI_MS_PPU_FX469_MS_ATT2	0x40027D78	FULL	Master attributes 2
PERI_MS_PPU_FX469_MS_ATT3	0x40027D7C	FULL	Master attributes 3

21.487 PPU_FX 470

Register Name	Address	Permission	Description
PERI_MS_PPU_FX470_SL_ADDR	0x40027D80	FULL	Slave region, base address
PERI_MS_PPU_FX470_SL_SIZE	0x40027D84	FULL	Slave region, size
PERI_MS_PPU_FX470_SL_ATT0	0x40027D90	FULL	Slave attributes 0
PERI_MS_PPU_FX470_SL_ATT1	0x40027D94	FULL	Slave attributes 1
PERI_MS_PPU_FX470_SL_ATT2	0x40027D98	FULL	Slave attributes 2
PERI_MS_PPU_FX470_SL_ATT3	0x40027D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX470_MS_ADDR	0x40027DA0	FULL	Master region, base address
PERI_MS_PPU_FX470_MS_SIZE	0x40027DA4	FULL	Master region, size
PERI_MS_PPU_FX470_MS_ATT0	0x40027DB0	FULL	Master attributes 0
PERI_MS_PPU_FX470_MS_ATT1	0x40027DB4	FULL	Master attributes 1
PERI_MS_PPU_FX470_MS_ATT2	0x40027DB8	FULL	Master attributes 2
PERI_MS_PPU_FX470_MS_ATT3	0x40027DBC	FULL	Master attributes 3

21.488 PPU_FX 471

Register Name	Address	Permission	Description
PERI_MS_PPU_FX471_SL_ADDR	0x40027DC0	FULL	Slave region, base address
PERI_MS_PPU_FX471_SL_SIZE	0x40027DC4	FULL	Slave region, size
PERI_MS_PPU_FX471_SL_ATT0	0x40027DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX471_SL_ATT1	0x40027DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX471_SL_ATT2	0x40027DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX471_SL_ATT3	0x40027DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX471_MS_ADDR	0x40027DE0	FULL	Master region, base address
PERI_MS_PPU_FX471_MS_SIZE	0x40027DE4	FULL	Master region, size
PERI_MS_PPU_FX471_MS_ATT0	0x40027DF0	FULL	Master attributes 0
PERI_MS_PPU_FX471_MS_ATT1	0x40027DF4	FULL	Master attributes 1
PERI_MS_PPU_FX471_MS_ATT2	0x40027DF8	FULL	Master attributes 2
PERI_MS_PPU_FX471_MS_ATT3	0x40027DFC	FULL	Master attributes 3

21.489 PPU_FX 472

Register Name	Address	Permission	Description
PERI_MS_PPU_FX472_SL_ADDR	0x40027E00	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX472_SL_SIZE	0x40027E04	FULL	Slave region, size
PERI_MS_PPU_FX472_SL_ATT0	0x40027E10	FULL	Slave attributes 0
PERI_MS_PPU_FX472_SL_ATT1	0x40027E14	FULL	Slave attributes 1
PERI_MS_PPU_FX472_SL_ATT2	0x40027E18	FULL	Slave attributes 2
PERI_MS_PPU_FX472_SL_ATT3	0x40027E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX472_MS_ADDR	0x40027E20	FULL	Master region, base address
PERI_MS_PPU_FX472_MS_SIZE	0x40027E24	FULL	Master region, size
PERI_MS_PPU_FX472_MS_ATT0	0x40027E30	FULL	Master attributes 0
PERI_MS_PPU_FX472_MS_ATT1	0x40027E34	FULL	Master attributes 1
PERI_MS_PPU_FX472_MS_ATT2	0x40027E38	FULL	Master attributes 2
PERI_MS_PPU_FX472_MS_ATT3	0x40027E3C	FULL	Master attributes 3

21.490 PPU_FX 473

Register Name	Address	Permission	Description
PERI_MS_PPU_FX473_SL_ADDR	0x40027E40	FULL	Slave region, base address
PERI_MS_PPU_FX473_SL_SIZE	0x40027E44	FULL	Slave region, size
PERI_MS_PPU_FX473_SL_ATT0	0x40027E50	FULL	Slave attributes 0
PERI_MS_PPU_FX473_SL_ATT1	0x40027E54	FULL	Slave attributes 1
PERI_MS_PPU_FX473_SL_ATT2	0x40027E58	FULL	Slave attributes 2
PERI_MS_PPU_FX473_SL_ATT3	0x40027E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX473_MS_ADDR	0x40027E60	FULL	Master region, base address
PERI_MS_PPU_FX473_MS_SIZE	0x40027E64	FULL	Master region, size
PERI_MS_PPU_FX473_MS_ATT0	0x40027E70	FULL	Master attributes 0
PERI_MS_PPU_FX473_MS_ATT1	0x40027E74	FULL	Master attributes 1
PERI_MS_PPU_FX473_MS_ATT2	0x40027E78	FULL	Master attributes 2
PERI_MS_PPU_FX473_MS_ATT3	0x40027E7C	FULL	Master attributes 3

21.491 PPU_FX 474

Register Name	Address	Permission	Description
PERI_MS_PPU_FX474_SL_ADDR	0x40027E80	FULL	Slave region, base address
PERI_MS_PPU_FX474_SL_SIZE	0x40027E84	FULL	Slave region, size
PERI_MS_PPU_FX474_SL_ATT0	0x40027E90	FULL	Slave attributes 0
PERI_MS_PPU_FX474_SL_ATT1	0x40027E94	FULL	Slave attributes 1
PERI_MS_PPU_FX474_SL_ATT2	0x40027E98	FULL	Slave attributes 2
PERI_MS_PPU_FX474_SL_ATT3	0x40027E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX474_MS_ADDR	0x40027EA0	FULL	Master region, base address
PERI_MS_PPU_FX474_MS_SIZE	0x40027EA4	FULL	Master region, size
PERI_MS_PPU_FX474_MS_ATT0	0x40027EB0	FULL	Master attributes 0
PERI_MS_PPU_FX474_MS_ATT1	0x40027EB4	FULL	Master attributes 1
PERI_MS_PPU_FX474_MS_ATT2	0x40027EB8	FULL	Master attributes 2
PERI_MS_PPU_FX474_MS_ATT3	0x40027EBC	FULL	Master attributes 3

21.492 PPU_FX 475

Register Name	Address	Permission	Description
PERI_MS_PPU_FX475_SL_ADDR	0x40027EC0	FULL	Slave region, base address
PERI_MS_PPU_FX475_SL_SIZE	0x40027EC4	FULL	Slave region, size
PERI_MS_PPU_FX475_SL_ATT0	0x40027ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX475_SL_ATT1	0x40027ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX475_SL_ATT2	0x40027ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX475_SL_ATT3	0x40027EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX475_MS_ADDR	0x40027EE0	FULL	Master region, base address
PERI_MS_PPU_FX475_MS_SIZE	0x40027EE4	FULL	Master region, size
PERI_MS_PPU_FX475_MS_ATT0	0x40027EF0	FULL	Master attributes 0
PERI_MS_PPU_FX475_MS_ATT1	0x40027EF4	FULL	Master attributes 1
PERI_MS_PPU_FX475_MS_ATT2	0x40027EF8	FULL	Master attributes 2
PERI_MS_PPU_FX475_MS_ATT3	0x40027EFC	FULL	Master attributes 3

21.493 PPU_FX 476

Register Name	Address	Permission	Description
PERI_MS_PPU_FX476_SL_ADDR	0x40027F00	FULL	Slave region, base address
PERI_MS_PPU_FX476_SL_SIZE	0x40027F04	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX476_SL_ATT0	0x40027F10	FULL	Slave attributes 0
PERI_MS_PPU_FX476_SL_ATT1	0x40027F14	FULL	Slave attributes 1
PERI_MS_PPU_FX476_SL_ATT2	0x40027F18	FULL	Slave attributes 2
PERI_MS_PPU_FX476_SL_ATT3	0x40027F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX476_MS_ADDR	0x40027F20	FULL	Master region, base address
PERI_MS_PPU_FX476_MS_SIZE	0x40027F24	FULL	Master region, size
PERI_MS_PPU_FX476_MS_ATT0	0x40027F30	FULL	Master attributes 0
PERI_MS_PPU_FX476_MS_ATT1	0x40027F34	FULL	Master attributes 1
PERI_MS_PPU_FX476_MS_ATT2	0x40027F38	FULL	Master attributes 2
PERI_MS_PPU_FX476_MS_ATT3	0x40027F3C	FULL	Master attributes 3

21.494 PPU_FX 477

Register Name	Address	Permission	Description
PERI_MS_PPU_FX477_SL_ADDR	0x40027F40	FULL	Slave region, base address
PERI_MS_PPU_FX477_SL_SIZE	0x40027F44	FULL	Slave region, size
PERI_MS_PPU_FX477_SL_ATT0	0x40027F50	FULL	Slave attributes 0
PERI_MS_PPU_FX477_SL_ATT1	0x40027F54	FULL	Slave attributes 1
PERI_MS_PPU_FX477_SL_ATT2	0x40027F58	FULL	Slave attributes 2
PERI_MS_PPU_FX477_SL_ATT3	0x40027F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX477_MS_ADDR	0x40027F60	FULL	Master region, base address
PERI_MS_PPU_FX477_MS_SIZE	0x40027F64	FULL	Master region, size
PERI_MS_PPU_FX477_MS_ATT0	0x40027F70	FULL	Master attributes 0
PERI_MS_PPU_FX477_MS_ATT1	0x40027F74	FULL	Master attributes 1
PERI_MS_PPU_FX477_MS_ATT2	0x40027F78	FULL	Master attributes 2
PERI_MS_PPU_FX477_MS_ATT3	0x40027F7C	FULL	Master attributes 3

21.495 PPU_FX 478

Register Name	Address	Permission	Description
PERI_MS_PPU_FX478_SL_ADDR	0x40027F80	FULL	Slave region, base address
PERI_MS_PPU_FX478_SL_SIZE	0x40027F84	FULL	Slave region, size
PERI_MS_PPU_FX478_SL_ATT0	0x40027F90	FULL	Slave attributes 0
PERI_MS_PPU_FX478_SL_ATT1	0x40027F94	FULL	Slave attributes 1
PERI_MS_PPU_FX478_SL_ATT2	0x40027F98	FULL	Slave attributes 2
PERI_MS_PPU_FX478_SL_ATT3	0x40027F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX478_MS_ADDR	0x40027FA0	FULL	Master region, base address
PERI_MS_PPU_FX478_MS_SIZE	0x40027FA4	FULL	Master region, size
PERI_MS_PPU_FX478_MS_ATT0	0x40027FB0	FULL	Master attributes 0
PERI_MS_PPU_FX478_MS_ATT1	0x40027FB4	FULL	Master attributes 1
PERI_MS_PPU_FX478_MS_ATT2	0x40027FB8	FULL	Master attributes 2
PERI_MS_PPU_FX478_MS_ATT3	0x40027FBC	FULL	Master attributes 3

21.496 PPU_FX 479

Register Name	Address	Permission	Description
PERI_MS_PPU_FX479_SL_ADDR	0x40027FC0	FULL	Slave region, base address
PERI_MS_PPU_FX479_SL_SIZE	0x40027FC4	FULL	Slave region, size
PERI_MS_PPU_FX479_SL_ATT0	0x40027FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX479_SL_ATT1	0x40027FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX479_SL_ATT2	0x40027FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX479_SL_ATT3	0x40027FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX479_MS_ADDR	0x40027FE0	FULL	Master region, base address
PERI_MS_PPU_FX479_MS_SIZE	0x40027FE4	FULL	Master region, size
PERI_MS_PPU_FX479_MS_ATT0	0x40027FF0	FULL	Master attributes 0
PERI_MS_PPU_FX479_MS_ATT1	0x40027FF4	FULL	Master attributes 1
PERI_MS_PPU_FX479_MS_ATT2	0x40027FF8	FULL	Master attributes 2
PERI_MS_PPU_FX479_MS_ATT3	0x40027FFC	FULL	Master attributes 3

21.497 PPU_FX 480

Register Name	Address	Permission	Description
PERI_MS_PPU_FX480_SL_ADDR	0x40028000	FULL	Slave region, base address
PERI_MS_PPU_FX480_SL_SIZE	0x40028004	FULL	Slave region, size
PERI_MS_PPU_FX480_SL_ATT0	0x40028010	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX480_SL_ATT1	0x40028014	FULL	Slave attributes 1
PERI_MS_PPU_FX480_SL_ATT2	0x40028018	FULL	Slave attributes 2
PERI_MS_PPU_FX480_SL_ATT3	0x4002801C	FULL	Slave attributes 3
PERI_MS_PPU_FX480_MS_ADDR	0x40028020	FULL	Master region, base address
PERI_MS_PPU_FX480_MS_SIZE	0x40028024	FULL	Master region, size
PERI_MS_PPU_FX480_MS_ATT0	0x40028030	FULL	Master attributes 0
PERI_MS_PPU_FX480_MS_ATT1	0x40028034	FULL	Master attributes 1
PERI_MS_PPU_FX480_MS_ATT2	0x40028038	FULL	Master attributes 2
PERI_MS_PPU_FX480_MS_ATT3	0x4002803C	FULL	Master attributes 3

21.498 PPU_FX 481

Register Name	Address	Permission	Description
PERI_MS_PPU_FX481_SL_ADDR	0x40028040	FULL	Slave region, base address
PERI_MS_PPU_FX481_SL_SIZE	0x40028044	FULL	Slave region, size
PERI_MS_PPU_FX481_SL_ATT0	0x40028050	FULL	Slave attributes 0
PERI_MS_PPU_FX481_SL_ATT1	0x40028054	FULL	Slave attributes 1
PERI_MS_PPU_FX481_SL_ATT2	0x40028058	FULL	Slave attributes 2
PERI_MS_PPU_FX481_SL_ATT3	0x4002805C	FULL	Slave attributes 3
PERI_MS_PPU_FX481_MS_ADDR	0x40028060	FULL	Master region, base address
PERI_MS_PPU_FX481_MS_SIZE	0x40028064	FULL	Master region, size
PERI_MS_PPU_FX481_MS_ATT0	0x40028070	FULL	Master attributes 0
PERI_MS_PPU_FX481_MS_ATT1	0x40028074	FULL	Master attributes 1
PERI_MS_PPU_FX481_MS_ATT2	0x40028078	FULL	Master attributes 2
PERI_MS_PPU_FX481_MS_ATT3	0x4002807C	FULL	Master attributes 3

21.499 PPU_FX 482

Register Name	Address	Permission	Description
PERI_MS_PPU_FX482_SL_ADDR	0x40028080	FULL	Slave region, base address
PERI_MS_PPU_FX482_SL_SIZE	0x40028084	FULL	Slave region, size
PERI_MS_PPU_FX482_SL_ATT0	0x40028090	FULL	Slave attributes 0
PERI_MS_PPU_FX482_SL_ATT1	0x40028094	FULL	Slave attributes 1
PERI_MS_PPU_FX482_SL_ATT2	0x40028098	FULL	Slave attributes 2
PERI_MS_PPU_FX482_SL_ATT3	0x4002809C	FULL	Slave attributes 3
PERI_MS_PPU_FX482_MS_ADDR	0x400280A0	FULL	Master region, base address
PERI_MS_PPU_FX482_MS_SIZE	0x400280A4	FULL	Master region, size
PERI_MS_PPU_FX482_MS_ATT0	0x400280B0	FULL	Master attributes 0
PERI_MS_PPU_FX482_MS_ATT1	0x400280B4	FULL	Master attributes 1
PERI_MS_PPU_FX482_MS_ATT2	0x400280B8	FULL	Master attributes 2
PERI_MS_PPU_FX482_MS_ATT3	0x400280BC	FULL	Master attributes 3

21.500 PPU_FX 483

Register Name	Address	Permission	Description
PERI_MS_PPU_FX483_SL_ADDR	0x400280C0	FULL	Slave region, base address
PERI_MS_PPU_FX483_SL_SIZE	0x400280C4	FULL	Slave region, size
PERI_MS_PPU_FX483_SL_ATT0	0x400280D0	FULL	Slave attributes 0
PERI_MS_PPU_FX483_SL_ATT1	0x400280D4	FULL	Slave attributes 1
PERI_MS_PPU_FX483_SL_ATT2	0x400280D8	FULL	Slave attributes 2
PERI_MS_PPU_FX483_SL_ATT3	0x400280DC	FULL	Slave attributes 3
PERI_MS_PPU_FX483_MS_ADDR	0x400280E0	FULL	Master region, base address
PERI_MS_PPU_FX483_MS_SIZE	0x400280E4	FULL	Master region, size
PERI_MS_PPU_FX483_MS_ATT0	0x400280F0	FULL	Master attributes 0
PERI_MS_PPU_FX483_MS_ATT1	0x400280F4	FULL	Master attributes 1
PERI_MS_PPU_FX483_MS_ATT2	0x400280F8	FULL	Master attributes 2
PERI_MS_PPU_FX483_MS_ATT3	0x400280FC	FULL	Master attributes 3

21.501 PPU_FX 484

Register Name	Address	Permission	Description
PERI_MS_PPU_FX484_SL_ADDR	0x40028100	FULL	Slave region, base address
PERI_MS_PPU_FX484_SL_SIZE	0x40028104	FULL	Slave region, size
PERI_MS_PPU_FX484_SL_ATT0	0x40028110	FULL	Slave attributes 0
PERI_MS_PPU_FX484_SL_ATT1	0x40028114	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX484_SL_ATT2	0x40028118	FULL	Slave attributes 2
PERI_MS_PPU_FX484_SL_ATT3	0x4002811C	FULL	Slave attributes 3
PERI_MS_PPU_FX484_MS_ADDR	0x40028120	FULL	Master region, base address
PERI_MS_PPU_FX484_MS_SIZE	0x40028124	FULL	Master region, size
PERI_MS_PPU_FX484_MS_ATT0	0x40028130	FULL	Master attributes 0
PERI_MS_PPU_FX484_MS_ATT1	0x40028134	FULL	Master attributes 1
PERI_MS_PPU_FX484_MS_ATT2	0x40028138	FULL	Master attributes 2
PERI_MS_PPU_FX484_MS_ATT3	0x4002813C	FULL	Master attributes 3

21.502 PPU_FX 485

Register Name	Address	Permission	Description
PERI_MS_PPU_FX485_SL_ADDR	0x40028140	FULL	Slave region, base address
PERI_MS_PPU_FX485_SL_SIZE	0x40028144	FULL	Slave region, size
PERI_MS_PPU_FX485_SL_ATT0	0x40028150	FULL	Slave attributes 0
PERI_MS_PPU_FX485_SL_ATT1	0x40028154	FULL	Slave attributes 1
PERI_MS_PPU_FX485_SL_ATT2	0x40028158	FULL	Slave attributes 2
PERI_MS_PPU_FX485_SL_ATT3	0x4002815C	FULL	Slave attributes 3
PERI_MS_PPU_FX485_MS_ADDR	0x40028160	FULL	Master region, base address
PERI_MS_PPU_FX485_MS_SIZE	0x40028164	FULL	Master region, size
PERI_MS_PPU_FX485_MS_ATT0	0x40028170	FULL	Master attributes 0
PERI_MS_PPU_FX485_MS_ATT1	0x40028174	FULL	Master attributes 1
PERI_MS_PPU_FX485_MS_ATT2	0x40028178	FULL	Master attributes 2
PERI_MS_PPU_FX485_MS_ATT3	0x4002817C	FULL	Master attributes 3

21.503 PPU_FX 486

Register Name	Address	Permission	Description
PERI_MS_PPU_FX486_SL_ADDR	0x40028180	FULL	Slave region, base address
PERI_MS_PPU_FX486_SL_SIZE	0x40028184	FULL	Slave region, size
PERI_MS_PPU_FX486_SL_ATT0	0x40028190	FULL	Slave attributes 0
PERI_MS_PPU_FX486_SL_ATT1	0x40028194	FULL	Slave attributes 1
PERI_MS_PPU_FX486_SL_ATT2	0x40028198	FULL	Slave attributes 2
PERI_MS_PPU_FX486_SL_ATT3	0x4002819C	FULL	Slave attributes 3
PERI_MS_PPU_FX486_MS_ADDR	0x400281A0	FULL	Master region, base address
PERI_MS_PPU_FX486_MS_SIZE	0x400281A4	FULL	Master region, size
PERI_MS_PPU_FX486_MS_ATT0	0x400281B0	FULL	Master attributes 0
PERI_MS_PPU_FX486_MS_ATT1	0x400281B4	FULL	Master attributes 1
PERI_MS_PPU_FX486_MS_ATT2	0x400281B8	FULL	Master attributes 2
PERI_MS_PPU_FX486_MS_ATT3	0x400281BC	FULL	Master attributes 3

21.504 PPU_FX 487

Register Name	Address	Permission	Description
PERI_MS_PPU_FX487_SL_ADDR	0x400281C0	FULL	Slave region, base address
PERI_MS_PPU_FX487_SL_SIZE	0x400281C4	FULL	Slave region, size
PERI_MS_PPU_FX487_SL_ATT0	0x400281D0	FULL	Slave attributes 0
PERI_MS_PPU_FX487_SL_ATT1	0x400281D4	FULL	Slave attributes 1
PERI_MS_PPU_FX487_SL_ATT2	0x400281D8	FULL	Slave attributes 2
PERI_MS_PPU_FX487_SL_ATT3	0x400281DC	FULL	Slave attributes 3
PERI_MS_PPU_FX487_MS_ADDR	0x400281E0	FULL	Master region, base address
PERI_MS_PPU_FX487_MS_SIZE	0x400281E4	FULL	Master region, size
PERI_MS_PPU_FX487_MS_ATT0	0x400281F0	FULL	Master attributes 0
PERI_MS_PPU_FX487_MS_ATT1	0x400281F4	FULL	Master attributes 1
PERI_MS_PPU_FX487_MS_ATT2	0x400281F8	FULL	Master attributes 2
PERI_MS_PPU_FX487_MS_ATT3	0x400281FC	FULL	Master attributes 3

21.505 PPU_FX 488

Register Name	Address	Permission	Description
PERI_MS_PPU_FX488_SL_ADDR	0x40028200	FULL	Slave region, base address
PERI_MS_PPU_FX488_SL_SIZE	0x40028204	FULL	Slave region, size
PERI_MS_PPU_FX488_SL_ATT0	0x40028210	FULL	Slave attributes 0
PERI_MS_PPU_FX488_SL_ATT1	0x40028214	FULL	Slave attributes 1
PERI_MS_PPU_FX488_SL_ATT2	0x40028218	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX488_SL_ATT3	0x4002821C	FULL	Slave attributes 3
PERI_MS_PPU_FX488_MS_ADDR	0x40028220	FULL	Master region, base address
PERI_MS_PPU_FX488_MS_SIZE	0x40028224	FULL	Master region, size
PERI_MS_PPU_FX488_MS_ATT0	0x40028230	FULL	Master attributes 0
PERI_MS_PPU_FX488_MS_ATT1	0x40028234	FULL	Master attributes 1
PERI_MS_PPU_FX488_MS_ATT2	0x40028238	FULL	Master attributes 2
PERI_MS_PPU_FX488_MS_ATT3	0x4002823C	FULL	Master attributes 3

21.506 PPU_FX 489

Register Name	Address	Permission	Description
PERI_MS_PPU_FX489_SL_ADDR	0x40028240	FULL	Slave region, base address
PERI_MS_PPU_FX489_SL_SIZE	0x40028244	FULL	Slave region, size
PERI_MS_PPU_FX489_SL_ATT0	0x40028250	FULL	Slave attributes 0
PERI_MS_PPU_FX489_SL_ATT1	0x40028254	FULL	Slave attributes 1
PERI_MS_PPU_FX489_SL_ATT2	0x40028258	FULL	Slave attributes 2
PERI_MS_PPU_FX489_SL_ATT3	0x4002825C	FULL	Slave attributes 3
PERI_MS_PPU_FX489_MS_ADDR	0x40028260	FULL	Master region, base address
PERI_MS_PPU_FX489_MS_SIZE	0x40028264	FULL	Master region, size
PERI_MS_PPU_FX489_MS_ATT0	0x40028270	FULL	Master attributes 0
PERI_MS_PPU_FX489_MS_ATT1	0x40028274	FULL	Master attributes 1
PERI_MS_PPU_FX489_MS_ATT2	0x40028278	FULL	Master attributes 2
PERI_MS_PPU_FX489_MS_ATT3	0x4002827C	FULL	Master attributes 3

21.507 PPU_FX 490

Register Name	Address	Permission	Description
PERI_MS_PPU_FX490_SL_ADDR	0x40028280	FULL	Slave region, base address
PERI_MS_PPU_FX490_SL_SIZE	0x40028284	FULL	Slave region, size
PERI_MS_PPU_FX490_SL_ATT0	0x40028290	FULL	Slave attributes 0
PERI_MS_PPU_FX490_SL_ATT1	0x40028294	FULL	Slave attributes 1
PERI_MS_PPU_FX490_SL_ATT2	0x40028298	FULL	Slave attributes 2
PERI_MS_PPU_FX490_SL_ATT3	0x4002829C	FULL	Slave attributes 3
PERI_MS_PPU_FX490_MS_ADDR	0x400282A0	FULL	Master region, base address
PERI_MS_PPU_FX490_MS_SIZE	0x400282A4	FULL	Master region, size
PERI_MS_PPU_FX490_MS_ATT0	0x400282B0	FULL	Master attributes 0
PERI_MS_PPU_FX490_MS_ATT1	0x400282B4	FULL	Master attributes 1
PERI_MS_PPU_FX490_MS_ATT2	0x400282B8	FULL	Master attributes 2
PERI_MS_PPU_FX490_MS_ATT3	0x400282BC	FULL	Master attributes 3

21.508 PPU_FX 491

Register Name	Address	Permission	Description
PERI_MS_PPU_FX491_SL_ADDR	0x400282C0	FULL	Slave region, base address
PERI_MS_PPU_FX491_SL_SIZE	0x400282C4	FULL	Slave region, size
PERI_MS_PPU_FX491_SL_ATT0	0x400282D0	FULL	Slave attributes 0
PERI_MS_PPU_FX491_SL_ATT1	0x400282D4	FULL	Slave attributes 1
PERI_MS_PPU_FX491_SL_ATT2	0x400282D8	FULL	Slave attributes 2
PERI_MS_PPU_FX491_SL_ATT3	0x400282DC	FULL	Slave attributes 3
PERI_MS_PPU_FX491_MS_ADDR	0x400282E0	FULL	Master region, base address
PERI_MS_PPU_FX491_MS_SIZE	0x400282E4	FULL	Master region, size
PERI_MS_PPU_FX491_MS_ATT0	0x400282F0	FULL	Master attributes 0
PERI_MS_PPU_FX491_MS_ATT1	0x400282F4	FULL	Master attributes 1
PERI_MS_PPU_FX491_MS_ATT2	0x400282F8	FULL	Master attributes 2
PERI_MS_PPU_FX491_MS_ATT3	0x400282FC	FULL	Master attributes 3

21.509 PPU_FX 492

Register Name	Address	Permission	Description
PERI_MS_PPU_FX492_SL_ADDR	0x40028300	FULL	Slave region, base address
PERI_MS_PPU_FX492_SL_SIZE	0x40028304	FULL	Slave region, size
PERI_MS_PPU_FX492_SL_ATT0	0x40028310	FULL	Slave attributes 0
PERI_MS_PPU_FX492_SL_ATT1	0x40028314	FULL	Slave attributes 1
PERI_MS_PPU_FX492_SL_ATT2	0x40028318	FULL	Slave attributes 2
PERI_MS_PPU_FX492_SL_ATT3	0x4002831C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX492_MS_ADDR	0x40028320	FULL	Master region, base address
PERI_MS_PPU_FX492_MS_SIZE	0x40028324	FULL	Master region, size
PERI_MS_PPU_FX492_MS_ATT0	0x40028330	FULL	Master attributes 0
PERI_MS_PPU_FX492_MS_ATT1	0x40028334	FULL	Master attributes 1
PERI_MS_PPU_FX492_MS_ATT2	0x40028338	FULL	Master attributes 2
PERI_MS_PPU_FX492_MS_ATT3	0x4002833C	FULL	Master attributes 3

21.510 PPU_FX 493

Register Name	Address	Permission	Description
PERI_MS_PPU_FX493_SL_ADDR	0x40028340	FULL	Slave region, base address
PERI_MS_PPU_FX493_SL_SIZE	0x40028344	FULL	Slave region, size
PERI_MS_PPU_FX493_SL_ATT0	0x40028350	FULL	Slave attributes 0
PERI_MS_PPU_FX493_SL_ATT1	0x40028354	FULL	Slave attributes 1
PERI_MS_PPU_FX493_SL_ATT2	0x40028358	FULL	Slave attributes 2
PERI_MS_PPU_FX493_SL_ATT3	0x4002835C	FULL	Slave attributes 3
PERI_MS_PPU_FX493_MS_ADDR	0x40028360	FULL	Master region, base address
PERI_MS_PPU_FX493_MS_SIZE	0x40028364	FULL	Master region, size
PERI_MS_PPU_FX493_MS_ATT0	0x40028370	FULL	Master attributes 0
PERI_MS_PPU_FX493_MS_ATT1	0x40028374	FULL	Master attributes 1
PERI_MS_PPU_FX493_MS_ATT2	0x40028378	FULL	Master attributes 2
PERI_MS_PPU_FX493_MS_ATT3	0x4002837C	FULL	Master attributes 3

21.511 PPU_FX 494

Register Name	Address	Permission	Description
PERI_MS_PPU_FX494_SL_ADDR	0x40028380	FULL	Slave region, base address
PERI_MS_PPU_FX494_SL_SIZE	0x40028384	FULL	Slave region, size
PERI_MS_PPU_FX494_SL_ATT0	0x40028390	FULL	Slave attributes 0
PERI_MS_PPU_FX494_SL_ATT1	0x40028394	FULL	Slave attributes 1
PERI_MS_PPU_FX494_SL_ATT2	0x40028398	FULL	Slave attributes 2
PERI_MS_PPU_FX494_SL_ATT3	0x4002839C	FULL	Slave attributes 3
PERI_MS_PPU_FX494_MS_ADDR	0x400283A0	FULL	Master region, base address
PERI_MS_PPU_FX494_MS_SIZE	0x400283A4	FULL	Master region, size
PERI_MS_PPU_FX494_MS_ATT0	0x400283B0	FULL	Master attributes 0
PERI_MS_PPU_FX494_MS_ATT1	0x400283B4	FULL	Master attributes 1
PERI_MS_PPU_FX494_MS_ATT2	0x400283B8	FULL	Master attributes 2
PERI_MS_PPU_FX494_MS_ATT3	0x400283BC	FULL	Master attributes 3

21.512 PPU_FX 495

Register Name	Address	Permission	Description
PERI_MS_PPU_FX495_SL_ADDR	0x400283C0	FULL	Slave region, base address
PERI_MS_PPU_FX495_SL_SIZE	0x400283C4	FULL	Slave region, size
PERI_MS_PPU_FX495_SL_ATT0	0x400283D0	FULL	Slave attributes 0
PERI_MS_PPU_FX495_SL_ATT1	0x400283D4	FULL	Slave attributes 1
PERI_MS_PPU_FX495_SL_ATT2	0x400283D8	FULL	Slave attributes 2
PERI_MS_PPU_FX495_SL_ATT3	0x400283DC	FULL	Slave attributes 3
PERI_MS_PPU_FX495_MS_ADDR	0x400283E0	FULL	Master region, base address
PERI_MS_PPU_FX495_MS_SIZE	0x400283E4	FULL	Master region, size
PERI_MS_PPU_FX495_MS_ATT0	0x400283F0	FULL	Master attributes 0
PERI_MS_PPU_FX495_MS_ATT1	0x400283F4	FULL	Master attributes 1
PERI_MS_PPU_FX495_MS_ATT2	0x400283F8	FULL	Master attributes 2
PERI_MS_PPU_FX495_MS_ATT3	0x400283FC	FULL	Master attributes 3

21.513 PPU_FX 496

Register Name	Address	Permission	Description
PERI_MS_PPU_FX496_SL_ADDR	0x40028400	FULL	Slave region, base address
PERI_MS_PPU_FX496_SL_SIZE	0x40028404	FULL	Slave region, size
PERI_MS_PPU_FX496_SL_ATT0	0x40028410	FULL	Slave attributes 0
PERI_MS_PPU_FX496_SL_ATT1	0x40028414	FULL	Slave attributes 1
PERI_MS_PPU_FX496_SL_ATT2	0x40028418	FULL	Slave attributes 2
PERI_MS_PPU_FX496_SL_ATT3	0x4002841C	FULL	Slave attributes 3
PERI_MS_PPU_FX496_MS_ADDR	0x40028420	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX496_MS_SIZE	0x40028424	FULL	Master region, size
PERI_MS_PPU_FX496_MS_ATT0	0x40028430	FULL	Master attributes 0
PERI_MS_PPU_FX496_MS_ATT1	0x40028434	FULL	Master attributes 1
PERI_MS_PPU_FX496_MS_ATT2	0x40028438	FULL	Master attributes 2
PERI_MS_PPU_FX496_MS_ATT3	0x4002843C	FULL	Master attributes 3

21.514 PPU_FX 497

Register Name	Address	Permission	Description
PERI_MS_PPU_FX497_SL_ADDR	0x40028440	FULL	Slave region, base address
PERI_MS_PPU_FX497_SL_SIZE	0x40028444	FULL	Slave region, size
PERI_MS_PPU_FX497_SL_ATT0	0x40028450	FULL	Slave attributes 0
PERI_MS_PPU_FX497_SL_ATT1	0x40028454	FULL	Slave attributes 1
PERI_MS_PPU_FX497_SL_ATT2	0x40028458	FULL	Slave attributes 2
PERI_MS_PPU_FX497_SL_ATT3	0x4002845C	FULL	Slave attributes 3
PERI_MS_PPU_FX497_MS_ADDR	0x40028460	FULL	Master region, base address
PERI_MS_PPU_FX497_MS_SIZE	0x40028464	FULL	Master region, size
PERI_MS_PPU_FX497_MS_ATT0	0x40028470	FULL	Master attributes 0
PERI_MS_PPU_FX497_MS_ATT1	0x40028474	FULL	Master attributes 1
PERI_MS_PPU_FX497_MS_ATT2	0x40028478	FULL	Master attributes 2
PERI_MS_PPU_FX497_MS_ATT3	0x4002847C	FULL	Master attributes 3

21.515 PPU_FX 498

Register Name	Address	Permission	Description
PERI_MS_PPU_FX498_SL_ADDR	0x40028480	FULL	Slave region, base address
PERI_MS_PPU_FX498_SL_SIZE	0x40028484	FULL	Slave region, size
PERI_MS_PPU_FX498_SL_ATT0	0x40028490	FULL	Slave attributes 0
PERI_MS_PPU_FX498_SL_ATT1	0x40028494	FULL	Slave attributes 1
PERI_MS_PPU_FX498_SL_ATT2	0x40028498	FULL	Slave attributes 2
PERI_MS_PPU_FX498_SL_ATT3	0x4002849C	FULL	Slave attributes 3
PERI_MS_PPU_FX498_MS_ADDR	0x400284A0	FULL	Master region, base address
PERI_MS_PPU_FX498_MS_SIZE	0x400284A4	FULL	Master region, size
PERI_MS_PPU_FX498_MS_ATT0	0x400284B0	FULL	Master attributes 0
PERI_MS_PPU_FX498_MS_ATT1	0x400284B4	FULL	Master attributes 1
PERI_MS_PPU_FX498_MS_ATT2	0x400284B8	FULL	Master attributes 2
PERI_MS_PPU_FX498_MS_ATT3	0x400284BC	FULL	Master attributes 3

21.516 PPU_FX 499

Register Name	Address	Permission	Description
PERI_MS_PPU_FX499_SL_ADDR	0x400284C0	FULL	Slave region, base address
PERI_MS_PPU_FX499_SL_SIZE	0x400284C4	FULL	Slave region, size
PERI_MS_PPU_FX499_SL_ATT0	0x400284D0	FULL	Slave attributes 0
PERI_MS_PPU_FX499_SL_ATT1	0x400284D4	FULL	Slave attributes 1
PERI_MS_PPU_FX499_SL_ATT2	0x400284D8	FULL	Slave attributes 2
PERI_MS_PPU_FX499_SL_ATT3	0x400284DC	FULL	Slave attributes 3
PERI_MS_PPU_FX499_MS_ADDR	0x400284E0	FULL	Master region, base address
PERI_MS_PPU_FX499_MS_SIZE	0x400284E4	FULL	Master region, size
PERI_MS_PPU_FX499_MS_ATT0	0x400284F0	FULL	Master attributes 0
PERI_MS_PPU_FX499_MS_ATT1	0x400284F4	FULL	Master attributes 1
PERI_MS_PPU_FX499_MS_ATT2	0x400284F8	FULL	Master attributes 2
PERI_MS_PPU_FX499_MS_ATT3	0x400284FC	FULL	Master attributes 3

21.517 PPU_FX 500

Register Name	Address	Permission	Description
PERI_MS_PPU_FX500_SL_ADDR	0x40028500	FULL	Slave region, base address
PERI_MS_PPU_FX500_SL_SIZE	0x40028504	FULL	Slave region, size
PERI_MS_PPU_FX500_SL_ATT0	0x40028510	FULL	Slave attributes 0
PERI_MS_PPU_FX500_SL_ATT1	0x40028514	FULL	Slave attributes 1
PERI_MS_PPU_FX500_SL_ATT2	0x40028518	FULL	Slave attributes 2
PERI_MS_PPU_FX500_SL_ATT3	0x4002851C	FULL	Slave attributes 3
PERI_MS_PPU_FX500_MS_ADDR	0x40028520	FULL	Master region, base address
PERI_MS_PPU_FX500_MS_SIZE	0x40028524	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX500_MS_ATT0	0x40028530	FULL	Master attributes 0
PERI_MS_PPU_FX500_MS_ATT1	0x40028534	FULL	Master attributes 1
PERI_MS_PPU_FX500_MS_ATT2	0x40028538	FULL	Master attributes 2
PERI_MS_PPU_FX500_MS_ATT3	0x4002853C	FULL	Master attributes 3

21.518 PPU_FX 501

Register Name	Address	Permission	Description
PERI_MS_PPU_FX501_SL_ADDR	0x40028540	FULL	Slave region, base address
PERI_MS_PPU_FX501_SL_SIZE	0x40028544	FULL	Slave region, size
PERI_MS_PPU_FX501_SL_ATT0	0x40028550	FULL	Slave attributes 0
PERI_MS_PPU_FX501_SL_ATT1	0x40028554	FULL	Slave attributes 1
PERI_MS_PPU_FX501_SL_ATT2	0x40028558	FULL	Slave attributes 2
PERI_MS_PPU_FX501_SL_ATT3	0x4002855C	FULL	Slave attributes 3
PERI_MS_PPU_FX501_MS_ADDR	0x40028560	FULL	Master region, base address
PERI_MS_PPU_FX501_MS_SIZE	0x40028564	FULL	Master region, size
PERI_MS_PPU_FX501_MS_ATT0	0x40028570	FULL	Master attributes 0
PERI_MS_PPU_FX501_MS_ATT1	0x40028574	FULL	Master attributes 1
PERI_MS_PPU_FX501_MS_ATT2	0x40028578	FULL	Master attributes 2
PERI_MS_PPU_FX501_MS_ATT3	0x4002857C	FULL	Master attributes 3

21.519 PPU_FX 502

Register Name	Address	Permission	Description
PERI_MS_PPU_FX502_SL_ADDR	0x40028580	FULL	Slave region, base address
PERI_MS_PPU_FX502_SL_SIZE	0x40028584	FULL	Slave region, size
PERI_MS_PPU_FX502_SL_ATT0	0x40028590	FULL	Slave attributes 0
PERI_MS_PPU_FX502_SL_ATT1	0x40028594	FULL	Slave attributes 1
PERI_MS_PPU_FX502_SL_ATT2	0x40028598	FULL	Slave attributes 2
PERI_MS_PPU_FX502_SL_ATT3	0x4002859C	FULL	Slave attributes 3
PERI_MS_PPU_FX502_MS_ADDR	0x400285A0	FULL	Master region, base address
PERI_MS_PPU_FX502_MS_SIZE	0x400285A4	FULL	Master region, size
PERI_MS_PPU_FX502_MS_ATT0	0x400285B0	FULL	Master attributes 0
PERI_MS_PPU_FX502_MS_ATT1	0x400285B4	FULL	Master attributes 1
PERI_MS_PPU_FX502_MS_ATT2	0x400285B8	FULL	Master attributes 2
PERI_MS_PPU_FX502_MS_ATT3	0x400285BC	FULL	Master attributes 3

21.520 PPU_FX 503

Register Name	Address	Permission	Description
PERI_MS_PPU_FX503_SL_ADDR	0x400285C0	FULL	Slave region, base address
PERI_MS_PPU_FX503_SL_SIZE	0x400285C4	FULL	Slave region, size
PERI_MS_PPU_FX503_SL_ATT0	0x400285D0	FULL	Slave attributes 0
PERI_MS_PPU_FX503_SL_ATT1	0x400285D4	FULL	Slave attributes 1
PERI_MS_PPU_FX503_SL_ATT2	0x400285D8	FULL	Slave attributes 2
PERI_MS_PPU_FX503_SL_ATT3	0x400285DC	FULL	Slave attributes 3
PERI_MS_PPU_FX503_MS_ADDR	0x400285E0	FULL	Master region, base address
PERI_MS_PPU_FX503_MS_SIZE	0x400285E4	FULL	Master region, size
PERI_MS_PPU_FX503_MS_ATT0	0x400285F0	FULL	Master attributes 0
PERI_MS_PPU_FX503_MS_ATT1	0x400285F4	FULL	Master attributes 1
PERI_MS_PPU_FX503_MS_ATT2	0x400285F8	FULL	Master attributes 2
PERI_MS_PPU_FX503_MS_ATT3	0x400285FC	FULL	Master attributes 3

21.521 PPU_FX 504

Register Name	Address	Permission	Description
PERI_MS_PPU_FX504_SL_ADDR	0x40028600	FULL	Slave region, base address
PERI_MS_PPU_FX504_SL_SIZE	0x40028604	FULL	Slave region, size
PERI_MS_PPU_FX504_SL_ATT0	0x40028610	FULL	Slave attributes 0
PERI_MS_PPU_FX504_SL_ATT1	0x40028614	FULL	Slave attributes 1
PERI_MS_PPU_FX504_SL_ATT2	0x40028618	FULL	Slave attributes 2
PERI_MS_PPU_FX504_SL_ATT3	0x4002861C	FULL	Slave attributes 3
PERI_MS_PPU_FX504_MS_ADDR	0x40028620	FULL	Master region, base address
PERI_MS_PPU_FX504_MS_SIZE	0x40028624	FULL	Master region, size
PERI_MS_PPU_FX504_MS_ATT0	0x40028630	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX504_MS_ATT1	0x40028634	FULL	Master attributes 1
PERI_MS_PPU_FX504_MS_ATT2	0x40028638	FULL	Master attributes 2
PERI_MS_PPU_FX504_MS_ATT3	0x4002863C	FULL	Master attributes 3

21.522 PPU_FX 505

Register Name	Address	Permission	Description
PERI_MS_PPU_FX505_SL_ADDR	0x40028640	FULL	Slave region, base address
PERI_MS_PPU_FX505_SL_SIZE	0x40028644	FULL	Slave region, size
PERI_MS_PPU_FX505_SL_ATT0	0x40028650	FULL	Slave attributes 0
PERI_MS_PPU_FX505_SL_ATT1	0x40028654	FULL	Slave attributes 1
PERI_MS_PPU_FX505_SL_ATT2	0x40028658	FULL	Slave attributes 2
PERI_MS_PPU_FX505_SL_ATT3	0x4002865C	FULL	Slave attributes 3
PERI_MS_PPU_FX505_MS_ADDR	0x40028660	FULL	Master region, base address
PERI_MS_PPU_FX505_MS_SIZE	0x40028664	FULL	Master region, size
PERI_MS_PPU_FX505_MS_ATT0	0x40028670	FULL	Master attributes 0
PERI_MS_PPU_FX505_MS_ATT1	0x40028674	FULL	Master attributes 1
PERI_MS_PPU_FX505_MS_ATT2	0x40028678	FULL	Master attributes 2
PERI_MS_PPU_FX505_MS_ATT3	0x4002867C	FULL	Master attributes 3

21.523 PPU_FX 506

Register Name	Address	Permission	Description
PERI_MS_PPU_FX506_SL_ADDR	0x40028680	FULL	Slave region, base address
PERI_MS_PPU_FX506_SL_SIZE	0x40028684	FULL	Slave region, size
PERI_MS_PPU_FX506_SL_ATT0	0x40028690	FULL	Slave attributes 0
PERI_MS_PPU_FX506_SL_ATT1	0x40028694	FULL	Slave attributes 1
PERI_MS_PPU_FX506_SL_ATT2	0x40028698	FULL	Slave attributes 2
PERI_MS_PPU_FX506_SL_ATT3	0x4002869C	FULL	Slave attributes 3
PERI_MS_PPU_FX506_MS_ADDR	0x400286A0	FULL	Master region, base address
PERI_MS_PPU_FX506_MS_SIZE	0x400286A4	FULL	Master region, size
PERI_MS_PPU_FX506_MS_ATT0	0x400286B0	FULL	Master attributes 0
PERI_MS_PPU_FX506_MS_ATT1	0x400286B4	FULL	Master attributes 1
PERI_MS_PPU_FX506_MS_ATT2	0x400286B8	FULL	Master attributes 2
PERI_MS_PPU_FX506_MS_ATT3	0x400286BC	FULL	Master attributes 3

21.524 PPU_FX 507

Register Name	Address	Permission	Description
PERI_MS_PPU_FX507_SL_ADDR	0x400286C0	FULL	Slave region, base address
PERI_MS_PPU_FX507_SL_SIZE	0x400286C4	FULL	Slave region, size
PERI_MS_PPU_FX507_SL_ATT0	0x400286D0	FULL	Slave attributes 0
PERI_MS_PPU_FX507_SL_ATT1	0x400286D4	FULL	Slave attributes 1
PERI_MS_PPU_FX507_SL_ATT2	0x400286D8	FULL	Slave attributes 2
PERI_MS_PPU_FX507_SL_ATT3	0x400286DC	FULL	Slave attributes 3
PERI_MS_PPU_FX507_MS_ADDR	0x400286E0	FULL	Master region, base address
PERI_MS_PPU_FX507_MS_SIZE	0x400286E4	FULL	Master region, size
PERI_MS_PPU_FX507_MS_ATT0	0x400286F0	FULL	Master attributes 0
PERI_MS_PPU_FX507_MS_ATT1	0x400286F4	FULL	Master attributes 1
PERI_MS_PPU_FX507_MS_ATT2	0x400286F8	FULL	Master attributes 2
PERI_MS_PPU_FX507_MS_ATT3	0x400286FC	FULL	Master attributes 3

21.525 PPU_FX 508

Register Name	Address	Permission	Description
PERI_MS_PPU_FX508_SL_ADDR	0x40028700	FULL	Slave region, base address
PERI_MS_PPU_FX508_SL_SIZE	0x40028704	FULL	Slave region, size
PERI_MS_PPU_FX508_SL_ATT0	0x40028710	FULL	Slave attributes 0
PERI_MS_PPU_FX508_SL_ATT1	0x40028714	FULL	Slave attributes 1
PERI_MS_PPU_FX508_SL_ATT2	0x40028718	FULL	Slave attributes 2
PERI_MS_PPU_FX508_SL_ATT3	0x4002871C	FULL	Slave attributes 3
PERI_MS_PPU_FX508_MS_ADDR	0x40028720	FULL	Master region, base address
PERI_MS_PPU_FX508_MS_SIZE	0x40028724	FULL	Master region, size
PERI_MS_PPU_FX508_MS_ATT0	0x40028730	FULL	Master attributes 0
PERI_MS_PPU_FX508_MS_ATT1	0x40028734	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX508_MS_ATT2	0x40028738	FULL	Master attributes 2
PERI_MS_PPU_FX508_MS_ATT3	0x4002873C	FULL	Master attributes 3

21.526 PPU_FX 509

Register Name	Address	Permission	Description
PERI_MS_PPU_FX509_SL_ADDR	0x40028740	FULL	Slave region, base address
PERI_MS_PPU_FX509_SL_SIZE	0x40028744	FULL	Slave region, size
PERI_MS_PPU_FX509_SL_ATT0	0x40028750	FULL	Slave attributes 0
PERI_MS_PPU_FX509_SL_ATT1	0x40028754	FULL	Slave attributes 1
PERI_MS_PPU_FX509_SL_ATT2	0x40028758	FULL	Slave attributes 2
PERI_MS_PPU_FX509_SL_ATT3	0x4002875C	FULL	Slave attributes 3
PERI_MS_PPU_FX509_MS_ADDR	0x40028760	FULL	Master region, base address
PERI_MS_PPU_FX509_MS_SIZE	0x40028764	FULL	Master region, size
PERI_MS_PPU_FX509_MS_ATT0	0x40028770	FULL	Master attributes 0
PERI_MS_PPU_FX509_MS_ATT1	0x40028774	FULL	Master attributes 1
PERI_MS_PPU_FX509_MS_ATT2	0x40028778	FULL	Master attributes 2
PERI_MS_PPU_FX509_MS_ATT3	0x4002877C	FULL	Master attributes 3

21.527 PPU_FX 510

Register Name	Address	Permission	Description
PERI_MS_PPU_FX510_SL_ADDR	0x40028780	FULL	Slave region, base address
PERI_MS_PPU_FX510_SL_SIZE	0x40028784	FULL	Slave region, size
PERI_MS_PPU_FX510_SL_ATT0	0x40028790	FULL	Slave attributes 0
PERI_MS_PPU_FX510_SL_ATT1	0x40028794	FULL	Slave attributes 1
PERI_MS_PPU_FX510_SL_ATT2	0x40028798	FULL	Slave attributes 2
PERI_MS_PPU_FX510_SL_ATT3	0x4002879C	FULL	Slave attributes 3
PERI_MS_PPU_FX510_MS_ADDR	0x400287A0	FULL	Master region, base address
PERI_MS_PPU_FX510_MS_SIZE	0x400287A4	FULL	Master region, size
PERI_MS_PPU_FX510_MS_ATT0	0x400287B0	FULL	Master attributes 0
PERI_MS_PPU_FX510_MS_ATT1	0x400287B4	FULL	Master attributes 1
PERI_MS_PPU_FX510_MS_ATT2	0x400287B8	FULL	Master attributes 2
PERI_MS_PPU_FX510_MS_ATT3	0x400287BC	FULL	Master attributes 3

21.528 PPU_FX 511

Register Name	Address	Permission	Description
PERI_MS_PPU_FX511_SL_ADDR	0x400287C0	FULL	Slave region, base address
PERI_MS_PPU_FX511_SL_SIZE	0x400287C4	FULL	Slave region, size
PERI_MS_PPU_FX511_SL_ATT0	0x400287D0	FULL	Slave attributes 0
PERI_MS_PPU_FX511_SL_ATT1	0x400287D4	FULL	Slave attributes 1
PERI_MS_PPU_FX511_SL_ATT2	0x400287D8	FULL	Slave attributes 2
PERI_MS_PPU_FX511_SL_ATT3	0x400287DC	FULL	Slave attributes 3
PERI_MS_PPU_FX511_MS_ADDR	0x400287E0	FULL	Master region, base address
PERI_MS_PPU_FX511_MS_SIZE	0x400287E4	FULL	Master region, size
PERI_MS_PPU_FX511_MS_ATT0	0x400287F0	FULL	Master attributes 0
PERI_MS_PPU_FX511_MS_ATT1	0x400287F4	FULL	Master attributes 1
PERI_MS_PPU_FX511_MS_ATT2	0x400287F8	FULL	Master attributes 2
PERI_MS_PPU_FX511_MS_ATT3	0x400287FC	FULL	Master attributes 3

21.529 PPU_FX 512

Register Name	Address	Permission	Description
PERI_MS_PPU_FX512_SL_ADDR	0x40028800	FULL	Slave region, base address
PERI_MS_PPU_FX512_SL_SIZE	0x40028804	FULL	Slave region, size
PERI_MS_PPU_FX512_SL_ATT0	0x40028810	FULL	Slave attributes 0
PERI_MS_PPU_FX512_SL_ATT1	0x40028814	FULL	Slave attributes 1
PERI_MS_PPU_FX512_SL_ATT2	0x40028818	FULL	Slave attributes 2
PERI_MS_PPU_FX512_SL_ATT3	0x4002881C	FULL	Slave attributes 3
PERI_MS_PPU_FX512_MS_ADDR	0x40028820	FULL	Master region, base address
PERI_MS_PPU_FX512_MS_SIZE	0x40028824	FULL	Master region, size
PERI_MS_PPU_FX512_MS_ATT0	0x40028830	FULL	Master attributes 0
PERI_MS_PPU_FX512_MS_ATT1	0x40028834	FULL	Master attributes 1
PERI_MS_PPU_FX512_MS_ATT2	0x40028838	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX512_MS_ATT3	0x4002883C	FULL	Master attributes 3

21.530 PPU_FX 513

Register Name	Address	Permission	Description
PERI_MS_PPU_FX513_SL_ADDR	0x40028840	FULL	Slave region, base address
PERI_MS_PPU_FX513_SL_SIZE	0x40028844	FULL	Slave region, size
PERI_MS_PPU_FX513_SL_ATT0	0x40028850	FULL	Slave attributes 0
PERI_MS_PPU_FX513_SL_ATT1	0x40028854	FULL	Slave attributes 1
PERI_MS_PPU_FX513_SL_ATT2	0x40028858	FULL	Slave attributes 2
PERI_MS_PPU_FX513_SL_ATT3	0x4002885C	FULL	Slave attributes 3
PERI_MS_PPU_FX513_MS_ADDR	0x40028860	FULL	Master region, base address
PERI_MS_PPU_FX513_MS_SIZE	0x40028864	FULL	Master region, size
PERI_MS_PPU_FX513_MS_ATT0	0x40028870	FULL	Master attributes 0
PERI_MS_PPU_FX513_MS_ATT1	0x40028874	FULL	Master attributes 1
PERI_MS_PPU_FX513_MS_ATT2	0x40028878	FULL	Master attributes 2
PERI_MS_PPU_FX513_MS_ATT3	0x4002887C	FULL	Master attributes 3

21.531 PPU_FX 514

Register Name	Address	Permission	Description
PERI_MS_PPU_FX514_SL_ADDR	0x40028880	FULL	Slave region, base address
PERI_MS_PPU_FX514_SL_SIZE	0x40028884	FULL	Slave region, size
PERI_MS_PPU_FX514_SL_ATT0	0x40028890	FULL	Slave attributes 0
PERI_MS_PPU_FX514_SL_ATT1	0x40028894	FULL	Slave attributes 1
PERI_MS_PPU_FX514_SL_ATT2	0x40028898	FULL	Slave attributes 2
PERI_MS_PPU_FX514_SL_ATT3	0x4002889C	FULL	Slave attributes 3
PERI_MS_PPU_FX514_MS_ADDR	0x400288A0	FULL	Master region, base address
PERI_MS_PPU_FX514_MS_SIZE	0x400288A4	FULL	Master region, size
PERI_MS_PPU_FX514_MS_ATT0	0x400288B0	FULL	Master attributes 0
PERI_MS_PPU_FX514_MS_ATT1	0x400288B4	FULL	Master attributes 1
PERI_MS_PPU_FX514_MS_ATT2	0x400288B8	FULL	Master attributes 2
PERI_MS_PPU_FX514_MS_ATT3	0x400288BC	FULL	Master attributes 3

21.532 PPU_FX 515

Register Name	Address	Permission	Description
PERI_MS_PPU_FX515_SL_ADDR	0x400288C0	FULL	Slave region, base address
PERI_MS_PPU_FX515_SL_SIZE	0x400288C4	FULL	Slave region, size
PERI_MS_PPU_FX515_SL_ATT0	0x400288D0	FULL	Slave attributes 0
PERI_MS_PPU_FX515_SL_ATT1	0x400288D4	FULL	Slave attributes 1
PERI_MS_PPU_FX515_SL_ATT2	0x400288D8	FULL	Slave attributes 2
PERI_MS_PPU_FX515_SL_ATT3	0x400288DC	FULL	Slave attributes 3
PERI_MS_PPU_FX515_MS_ADDR	0x400288E0	FULL	Master region, base address
PERI_MS_PPU_FX515_MS_SIZE	0x400288E4	FULL	Master region, size
PERI_MS_PPU_FX515_MS_ATT0	0x400288F0	FULL	Master attributes 0
PERI_MS_PPU_FX515_MS_ATT1	0x400288F4	FULL	Master attributes 1
PERI_MS_PPU_FX515_MS_ATT2	0x400288F8	FULL	Master attributes 2
PERI_MS_PPU_FX515_MS_ATT3	0x400288FC	FULL	Master attributes 3

21.533 PPU_FX 516

Register Name	Address	Permission	Description
PERI_MS_PPU_FX516_SL_ADDR	0x40028900	FULL	Slave region, base address
PERI_MS_PPU_FX516_SL_SIZE	0x40028904	FULL	Slave region, size
PERI_MS_PPU_FX516_SL_ATT0	0x40028910	FULL	Slave attributes 0
PERI_MS_PPU_FX516_SL_ATT1	0x40028914	FULL	Slave attributes 1
PERI_MS_PPU_FX516_SL_ATT2	0x40028918	FULL	Slave attributes 2
PERI_MS_PPU_FX516_SL_ATT3	0x4002891C	FULL	Slave attributes 3
PERI_MS_PPU_FX516_MS_ADDR	0x40028920	FULL	Master region, base address
PERI_MS_PPU_FX516_MS_SIZE	0x40028924	FULL	Master region, size
PERI_MS_PPU_FX516_MS_ATT0	0x40028930	FULL	Master attributes 0
PERI_MS_PPU_FX516_MS_ATT1	0x40028934	FULL	Master attributes 1
PERI_MS_PPU_FX516_MS_ATT2	0x40028938	FULL	Master attributes 2
PERI_MS_PPU_FX516_MS_ATT3	0x4002893C	FULL	Master attributes 3

21.534 PPU_FX 517

Register Name	Address	Permission	Description
PERI_MS_PPU_FX517_SL_ADDR	0x40028940	FULL	Slave region, base address
PERI_MS_PPU_FX517_SL_SIZE	0x40028944	FULL	Slave region, size
PERI_MS_PPU_FX517_SL_ATT0	0x40028950	FULL	Slave attributes 0
PERI_MS_PPU_FX517_SL_ATT1	0x40028954	FULL	Slave attributes 1
PERI_MS_PPU_FX517_SL_ATT2	0x40028958	FULL	Slave attributes 2
PERI_MS_PPU_FX517_SL_ATT3	0x4002895C	FULL	Slave attributes 3
PERI_MS_PPU_FX517_MS_ADDR	0x40028960	FULL	Master region, base address
PERI_MS_PPU_FX517_MS_SIZE	0x40028964	FULL	Master region, size
PERI_MS_PPU_FX517_MS_ATT0	0x40028970	FULL	Master attributes 0
PERI_MS_PPU_FX517_MS_ATT1	0x40028974	FULL	Master attributes 1
PERI_MS_PPU_FX517_MS_ATT2	0x40028978	FULL	Master attributes 2
PERI_MS_PPU_FX517_MS_ATT3	0x4002897C	FULL	Master attributes 3

21.535 PPU_FX 518

Register Name	Address	Permission	Description
PERI_MS_PPU_FX518_SL_ADDR	0x40028980	FULL	Slave region, base address
PERI_MS_PPU_FX518_SL_SIZE	0x40028984	FULL	Slave region, size
PERI_MS_PPU_FX518_SL_ATT0	0x40028990	FULL	Slave attributes 0
PERI_MS_PPU_FX518_SL_ATT1	0x40028994	FULL	Slave attributes 1
PERI_MS_PPU_FX518_SL_ATT2	0x40028998	FULL	Slave attributes 2
PERI_MS_PPU_FX518_SL_ATT3	0x4002899C	FULL	Slave attributes 3
PERI_MS_PPU_FX518_MS_ADDR	0x400289A0	FULL	Master region, base address
PERI_MS_PPU_FX518_MS_SIZE	0x400289A4	FULL	Master region, size
PERI_MS_PPU_FX518_MS_ATT0	0x400289B0	FULL	Master attributes 0
PERI_MS_PPU_FX518_MS_ATT1	0x400289B4	FULL	Master attributes 1
PERI_MS_PPU_FX518_MS_ATT2	0x400289B8	FULL	Master attributes 2
PERI_MS_PPU_FX518_MS_ATT3	0x400289BC	FULL	Master attributes 3

21.536 PPU_FX 519

Register Name	Address	Permission	Description
PERI_MS_PPU_FX519_SL_ADDR	0x400289C0	FULL	Slave region, base address
PERI_MS_PPU_FX519_SL_SIZE	0x400289C4	FULL	Slave region, size
PERI_MS_PPU_FX519_SL_ATT0	0x400289D0	FULL	Slave attributes 0
PERI_MS_PPU_FX519_SL_ATT1	0x400289D4	FULL	Slave attributes 1
PERI_MS_PPU_FX519_SL_ATT2	0x400289D8	FULL	Slave attributes 2
PERI_MS_PPU_FX519_SL_ATT3	0x400289DC	FULL	Slave attributes 3
PERI_MS_PPU_FX519_MS_ADDR	0x400289E0	FULL	Master region, base address
PERI_MS_PPU_FX519_MS_SIZE	0x400289E4	FULL	Master region, size
PERI_MS_PPU_FX519_MS_ATT0	0x400289F0	FULL	Master attributes 0
PERI_MS_PPU_FX519_MS_ATT1	0x400289F4	FULL	Master attributes 1
PERI_MS_PPU_FX519_MS_ATT2	0x400289F8	FULL	Master attributes 2
PERI_MS_PPU_FX519_MS_ATT3	0x400289FC	FULL	Master attributes 3

21.537 PPU_FX 520

Register Name	Address	Permission	Description
PERI_MS_PPU_FX520_SL_ADDR	0x40028A00	FULL	Slave region, base address
PERI_MS_PPU_FX520_SL_SIZE	0x40028A04	FULL	Slave region, size
PERI_MS_PPU_FX520_SL_ATT0	0x40028A10	FULL	Slave attributes 0
PERI_MS_PPU_FX520_SL_ATT1	0x40028A14	FULL	Slave attributes 1
PERI_MS_PPU_FX520_SL_ATT2	0x40028A18	FULL	Slave attributes 2
PERI_MS_PPU_FX520_SL_ATT3	0x40028A1C	FULL	Slave attributes 3
PERI_MS_PPU_FX520_MS_ADDR	0x40028A20	FULL	Master region, base address
PERI_MS_PPU_FX520_MS_SIZE	0x40028A24	FULL	Master region, size
PERI_MS_PPU_FX520_MS_ATT0	0x40028A30	FULL	Master attributes 0
PERI_MS_PPU_FX520_MS_ATT1	0x40028A34	FULL	Master attributes 1
PERI_MS_PPU_FX520_MS_ATT2	0x40028A38	FULL	Master attributes 2
PERI_MS_PPU_FX520_MS_ATT3	0x40028A3C	FULL	Master attributes 3

21.538 PPU_FX 521

Register Name	Address	Permission	Description
PERI_MS_PPU_FX521_SL_ADDR	0x40028A40	FULL	Slave region, base address
PERI_MS_PPU_FX521_SL_SIZE	0x40028A44	FULL	Slave region, size
PERI_MS_PPU_FX521_SL_ATT0	0x40028A50	FULL	Slave attributes 0
PERI_MS_PPU_FX521_SL_ATT1	0x40028A54	FULL	Slave attributes 1
PERI_MS_PPU_FX521_SL_ATT2	0x40028A58	FULL	Slave attributes 2
PERI_MS_PPU_FX521_SL_ATT3	0x40028A5C	FULL	Slave attributes 3
PERI_MS_PPU_FX521_MS_ADDR	0x40028A60	FULL	Master region, base address
PERI_MS_PPU_FX521_MS_SIZE	0x40028A64	FULL	Master region, size
PERI_MS_PPU_FX521_MS_ATT0	0x40028A70	FULL	Master attributes 0
PERI_MS_PPU_FX521_MS_ATT1	0x40028A74	FULL	Master attributes 1
PERI_MS_PPU_FX521_MS_ATT2	0x40028A78	FULL	Master attributes 2
PERI_MS_PPU_FX521_MS_ATT3	0x40028A7C	FULL	Master attributes 3

21.539 PPU_FX 522

Register Name	Address	Permission	Description
PERI_MS_PPU_FX522_SL_ADDR	0x40028A80	FULL	Slave region, base address
PERI_MS_PPU_FX522_SL_SIZE	0x40028A84	FULL	Slave region, size
PERI_MS_PPU_FX522_SL_ATT0	0x40028A90	FULL	Slave attributes 0
PERI_MS_PPU_FX522_SL_ATT1	0x40028A94	FULL	Slave attributes 1
PERI_MS_PPU_FX522_SL_ATT2	0x40028A98	FULL	Slave attributes 2
PERI_MS_PPU_FX522_SL_ATT3	0x40028A9C	FULL	Slave attributes 3
PERI_MS_PPU_FX522_MS_ADDR	0x40028AA0	FULL	Master region, base address
PERI_MS_PPU_FX522_MS_SIZE	0x40028AA4	FULL	Master region, size
PERI_MS_PPU_FX522_MS_ATT0	0x40028AB0	FULL	Master attributes 0
PERI_MS_PPU_FX522_MS_ATT1	0x40028AB4	FULL	Master attributes 1
PERI_MS_PPU_FX522_MS_ATT2	0x40028AB8	FULL	Master attributes 2
PERI_MS_PPU_FX522_MS_ATT3	0x40028ABC	FULL	Master attributes 3

21.540 PPU_FX 523

Register Name	Address	Permission	Description
PERI_MS_PPU_FX523_SL_ADDR	0x40028AC0	FULL	Slave region, base address
PERI_MS_PPU_FX523_SL_SIZE	0x40028AC4	FULL	Slave region, size
PERI_MS_PPU_FX523_SL_ATT0	0x40028AD0	FULL	Slave attributes 0
PERI_MS_PPU_FX523_SL_ATT1	0x40028AD4	FULL	Slave attributes 1
PERI_MS_PPU_FX523_SL_ATT2	0x40028AD8	FULL	Slave attributes 2
PERI_MS_PPU_FX523_SL_ATT3	0x40028ADC	FULL	Slave attributes 3
PERI_MS_PPU_FX523_MS_ADDR	0x40028AE0	FULL	Master region, base address
PERI_MS_PPU_FX523_MS_SIZE	0x40028AE4	FULL	Master region, size
PERI_MS_PPU_FX523_MS_ATT0	0x40028AF0	FULL	Master attributes 0
PERI_MS_PPU_FX523_MS_ATT1	0x40028AF4	FULL	Master attributes 1
PERI_MS_PPU_FX523_MS_ATT2	0x40028AF8	FULL	Master attributes 2
PERI_MS_PPU_FX523_MS_ATT3	0x40028AFC	FULL	Master attributes 3

21.541 PPU_FX 524

Register Name	Address	Permission	Description
PERI_MS_PPU_FX524_SL_ADDR	0x40028B00	FULL	Slave region, base address
PERI_MS_PPU_FX524_SL_SIZE	0x40028B04	FULL	Slave region, size
PERI_MS_PPU_FX524_SL_ATT0	0x40028B10	FULL	Slave attributes 0
PERI_MS_PPU_FX524_SL_ATT1	0x40028B14	FULL	Slave attributes 1
PERI_MS_PPU_FX524_SL_ATT2	0x40028B18	FULL	Slave attributes 2
PERI_MS_PPU_FX524_SL_ATT3	0x40028B1C	FULL	Slave attributes 3
PERI_MS_PPU_FX524_MS_ADDR	0x40028B20	FULL	Master region, base address
PERI_MS_PPU_FX524_MS_SIZE	0x40028B24	FULL	Master region, size
PERI_MS_PPU_FX524_MS_ATT0	0x40028B30	FULL	Master attributes 0
PERI_MS_PPU_FX524_MS_ATT1	0x40028B34	FULL	Master attributes 1
PERI_MS_PPU_FX524_MS_ATT2	0x40028B38	FULL	Master attributes 2
PERI_MS_PPU_FX524_MS_ATT3	0x40028B3C	FULL	Master attributes 3

21.542 PPU_FX 525

Register Name	Address	Permission	Description
PERI_MS_PPU_FX525_SL_ADDR	0x40028B40	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX525_SL_SIZE	0x40028B44	FULL	Slave region, size
PERI_MS_PPU_FX525_SL_ATT0	0x40028B50	FULL	Slave attributes 0
PERI_MS_PPU_FX525_SL_ATT1	0x40028B54	FULL	Slave attributes 1
PERI_MS_PPU_FX525_SL_ATT2	0x40028B58	FULL	Slave attributes 2
PERI_MS_PPU_FX525_SL_ATT3	0x40028B5C	FULL	Slave attributes 3
PERI_MS_PPU_FX525_MS_ADDR	0x40028B60	FULL	Master region, base address
PERI_MS_PPU_FX525_MS_SIZE	0x40028B64	FULL	Master region, size
PERI_MS_PPU_FX525_MS_ATT0	0x40028B70	FULL	Master attributes 0
PERI_MS_PPU_FX525_MS_ATT1	0x40028B74	FULL	Master attributes 1
PERI_MS_PPU_FX525_MS_ATT2	0x40028B78	FULL	Master attributes 2
PERI_MS_PPU_FX525_MS_ATT3	0x40028B7C	FULL	Master attributes 3

21.543 PPU_FX 526

Register Name	Address	Permission	Description
PERI_MS_PPU_FX526_SL_ADDR	0x40028B80	FULL	Slave region, base address
PERI_MS_PPU_FX526_SL_SIZE	0x40028B84	FULL	Slave region, size
PERI_MS_PPU_FX526_SL_ATT0	0x40028B90	FULL	Slave attributes 0
PERI_MS_PPU_FX526_SL_ATT1	0x40028B94	FULL	Slave attributes 1
PERI_MS_PPU_FX526_SL_ATT2	0x40028B98	FULL	Slave attributes 2
PERI_MS_PPU_FX526_SL_ATT3	0x40028B9C	FULL	Slave attributes 3
PERI_MS_PPU_FX526_MS_ADDR	0x40028BA0	FULL	Master region, base address
PERI_MS_PPU_FX526_MS_SIZE	0x40028BA4	FULL	Master region, size
PERI_MS_PPU_FX526_MS_ATT0	0x40028BB0	FULL	Master attributes 0
PERI_MS_PPU_FX526_MS_ATT1	0x40028BB4	FULL	Master attributes 1
PERI_MS_PPU_FX526_MS_ATT2	0x40028BB8	FULL	Master attributes 2
PERI_MS_PPU_FX526_MS_ATT3	0x40028BBC	FULL	Master attributes 3

21.544 PPU_FX 527

Register Name	Address	Permission	Description
PERI_MS_PPU_FX527_SL_ADDR	0x40028BC0	FULL	Slave region, base address
PERI_MS_PPU_FX527_SL_SIZE	0x40028BC4	FULL	Slave region, size
PERI_MS_PPU_FX527_SL_ATT0	0x40028BD0	FULL	Slave attributes 0
PERI_MS_PPU_FX527_SL_ATT1	0x40028BD4	FULL	Slave attributes 1
PERI_MS_PPU_FX527_SL_ATT2	0x40028BD8	FULL	Slave attributes 2
PERI_MS_PPU_FX527_SL_ATT3	0x40028BDC	FULL	Slave attributes 3
PERI_MS_PPU_FX527_MS_ADDR	0x40028BE0	FULL	Master region, base address
PERI_MS_PPU_FX527_MS_SIZE	0x40028BE4	FULL	Master region, size
PERI_MS_PPU_FX527_MS_ATT0	0x40028BF0	FULL	Master attributes 0
PERI_MS_PPU_FX527_MS_ATT1	0x40028BF4	FULL	Master attributes 1
PERI_MS_PPU_FX527_MS_ATT2	0x40028BF8	FULL	Master attributes 2
PERI_MS_PPU_FX527_MS_ATT3	0x40028BFC	FULL	Master attributes 3

21.545 PPU_FX 528

Register Name	Address	Permission	Description
PERI_MS_PPU_FX528_SL_ADDR	0x40028C00	FULL	Slave region, base address
PERI_MS_PPU_FX528_SL_SIZE	0x40028C04	FULL	Slave region, size
PERI_MS_PPU_FX528_SL_ATT0	0x40028C10	FULL	Slave attributes 0
PERI_MS_PPU_FX528_SL_ATT1	0x40028C14	FULL	Slave attributes 1
PERI_MS_PPU_FX528_SL_ATT2	0x40028C18	FULL	Slave attributes 2
PERI_MS_PPU_FX528_SL_ATT3	0x40028C1C	FULL	Slave attributes 3
PERI_MS_PPU_FX528_MS_ADDR	0x40028C20	FULL	Master region, base address
PERI_MS_PPU_FX528_MS_SIZE	0x40028C24	FULL	Master region, size
PERI_MS_PPU_FX528_MS_ATT0	0x40028C30	FULL	Master attributes 0
PERI_MS_PPU_FX528_MS_ATT1	0x40028C34	FULL	Master attributes 1
PERI_MS_PPU_FX528_MS_ATT2	0x40028C38	FULL	Master attributes 2
PERI_MS_PPU_FX528_MS_ATT3	0x40028C3C	FULL	Master attributes 3

21.546 PPU_FX 529

Register Name	Address	Permission	Description
PERI_MS_PPU_FX529_SL_ADDR	0x40028C40	FULL	Slave region, base address
PERI_MS_PPU_FX529_SL_SIZE	0x40028C44	FULL	Slave region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX529_SL_ATT0	0x40028C50	FULL	Slave attributes 0
PERI_MS_PPU_FX529_SL_ATT1	0x40028C54	FULL	Slave attributes 1
PERI_MS_PPU_FX529_SL_ATT2	0x40028C58	FULL	Slave attributes 2
PERI_MS_PPU_FX529_SL_ATT3	0x40028C5C	FULL	Slave attributes 3
PERI_MS_PPU_FX529_MS_ADDR	0x40028C60	FULL	Master region, base address
PERI_MS_PPU_FX529_MS_SIZE	0x40028C64	FULL	Master region, size
PERI_MS_PPU_FX529_MS_ATT0	0x40028C70	FULL	Master attributes 0
PERI_MS_PPU_FX529_MS_ATT1	0x40028C74	FULL	Master attributes 1
PERI_MS_PPU_FX529_MS_ATT2	0x40028C78	FULL	Master attributes 2
PERI_MS_PPU_FX529_MS_ATT3	0x40028C7C	FULL	Master attributes 3

21.547 PPU_FX 530

Register Name	Address	Permission	Description
PERI_MS_PPU_FX530_SL_ADDR	0x40028C80	FULL	Slave region, base address
PERI_MS_PPU_FX530_SL_SIZE	0x40028C84	FULL	Slave region, size
PERI_MS_PPU_FX530_SL_ATT0	0x40028C90	FULL	Slave attributes 0
PERI_MS_PPU_FX530_SL_ATT1	0x40028C94	FULL	Slave attributes 1
PERI_MS_PPU_FX530_SL_ATT2	0x40028C98	FULL	Slave attributes 2
PERI_MS_PPU_FX530_SL_ATT3	0x40028C9C	FULL	Slave attributes 3
PERI_MS_PPU_FX530_MS_ADDR	0x40028CA0	FULL	Master region, base address
PERI_MS_PPU_FX530_MS_SIZE	0x40028CA4	FULL	Master region, size
PERI_MS_PPU_FX530_MS_ATT0	0x40028CB0	FULL	Master attributes 0
PERI_MS_PPU_FX530_MS_ATT1	0x40028CB4	FULL	Master attributes 1
PERI_MS_PPU_FX530_MS_ATT2	0x40028CB8	FULL	Master attributes 2
PERI_MS_PPU_FX530_MS_ATT3	0x40028CBC	FULL	Master attributes 3

21.548 PPU_FX 531

Register Name	Address	Permission	Description
PERI_MS_PPU_FX531_SL_ADDR	0x40028CC0	FULL	Slave region, base address
PERI_MS_PPU_FX531_SL_SIZE	0x40028CC4	FULL	Slave region, size
PERI_MS_PPU_FX531_SL_ATT0	0x40028CD0	FULL	Slave attributes 0
PERI_MS_PPU_FX531_SL_ATT1	0x40028CD4	FULL	Slave attributes 1
PERI_MS_PPU_FX531_SL_ATT2	0x40028CD8	FULL	Slave attributes 2
PERI_MS_PPU_FX531_SL_ATT3	0x40028CDC	FULL	Slave attributes 3
PERI_MS_PPU_FX531_MS_ADDR	0x40028CE0	FULL	Master region, base address
PERI_MS_PPU_FX531_MS_SIZE	0x40028CE4	FULL	Master region, size
PERI_MS_PPU_FX531_MS_ATT0	0x40028CF0	FULL	Master attributes 0
PERI_MS_PPU_FX531_MS_ATT1	0x40028CF4	FULL	Master attributes 1
PERI_MS_PPU_FX531_MS_ATT2	0x40028CF8	FULL	Master attributes 2
PERI_MS_PPU_FX531_MS_ATT3	0x40028CFC	FULL	Master attributes 3

21.549 PPU_FX 532

Register Name	Address	Permission	Description
PERI_MS_PPU_FX532_SL_ADDR	0x40028D00	FULL	Slave region, base address
PERI_MS_PPU_FX532_SL_SIZE	0x40028D04	FULL	Slave region, size
PERI_MS_PPU_FX532_SL_ATT0	0x40028D10	FULL	Slave attributes 0
PERI_MS_PPU_FX532_SL_ATT1	0x40028D14	FULL	Slave attributes 1
PERI_MS_PPU_FX532_SL_ATT2	0x40028D18	FULL	Slave attributes 2
PERI_MS_PPU_FX532_SL_ATT3	0x40028D1C	FULL	Slave attributes 3
PERI_MS_PPU_FX532_MS_ADDR	0x40028D20	FULL	Master region, base address
PERI_MS_PPU_FX532_MS_SIZE	0x40028D24	FULL	Master region, size
PERI_MS_PPU_FX532_MS_ATT0	0x40028D30	FULL	Master attributes 0
PERI_MS_PPU_FX532_MS_ATT1	0x40028D34	FULL	Master attributes 1
PERI_MS_PPU_FX532_MS_ATT2	0x40028D38	FULL	Master attributes 2
PERI_MS_PPU_FX532_MS_ATT3	0x40028D3C	FULL	Master attributes 3

21.550 PPU_FX 533

Register Name	Address	Permission	Description
PERI_MS_PPU_FX533_SL_ADDR	0x40028D40	FULL	Slave region, base address
PERI_MS_PPU_FX533_SL_SIZE	0x40028D44	FULL	Slave region, size
PERI_MS_PPU_FX533_SL_ATT0	0x40028D50	FULL	Slave attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX533_SL_ATT1	0x40028D54	FULL	Slave attributes 1
PERI_MS_PPU_FX533_SL_ATT2	0x40028D58	FULL	Slave attributes 2
PERI_MS_PPU_FX533_SL_ATT3	0x40028D5C	FULL	Slave attributes 3
PERI_MS_PPU_FX533_MS_ADDR	0x40028D60	FULL	Master region, base address
PERI_MS_PPU_FX533_MS_SIZE	0x40028D64	FULL	Master region, size
PERI_MS_PPU_FX533_MS_ATT0	0x40028D70	FULL	Master attributes 0
PERI_MS_PPU_FX533_MS_ATT1	0x40028D74	FULL	Master attributes 1
PERI_MS_PPU_FX533_MS_ATT2	0x40028D78	FULL	Master attributes 2
PERI_MS_PPU_FX533_MS_ATT3	0x40028D7C	FULL	Master attributes 3

21.551 PPU_FX 534

Register Name	Address	Permission	Description
PERI_MS_PPU_FX534_SL_ADDR	0x40028D80	FULL	Slave region, base address
PERI_MS_PPU_FX534_SL_SIZE	0x40028D84	FULL	Slave region, size
PERI_MS_PPU_FX534_SL_ATT0	0x40028D90	FULL	Slave attributes 0
PERI_MS_PPU_FX534_SL_ATT1	0x40028D94	FULL	Slave attributes 1
PERI_MS_PPU_FX534_SL_ATT2	0x40028D98	FULL	Slave attributes 2
PERI_MS_PPU_FX534_SL_ATT3	0x40028D9C	FULL	Slave attributes 3
PERI_MS_PPU_FX534_MS_ADDR	0x40028DA0	FULL	Master region, base address
PERI_MS_PPU_FX534_MS_SIZE	0x40028DA4	FULL	Master region, size
PERI_MS_PPU_FX534_MS_ATT0	0x40028DB0	FULL	Master attributes 0
PERI_MS_PPU_FX534_MS_ATT1	0x40028DB4	FULL	Master attributes 1
PERI_MS_PPU_FX534_MS_ATT2	0x40028DB8	FULL	Master attributes 2
PERI_MS_PPU_FX534_MS_ATT3	0x40028DBC	FULL	Master attributes 3

21.552 PPU_FX 535

Register Name	Address	Permission	Description
PERI_MS_PPU_FX535_SL_ADDR	0x40028DC0	FULL	Slave region, base address
PERI_MS_PPU_FX535_SL_SIZE	0x40028DC4	FULL	Slave region, size
PERI_MS_PPU_FX535_SL_ATT0	0x40028DD0	FULL	Slave attributes 0
PERI_MS_PPU_FX535_SL_ATT1	0x40028DD4	FULL	Slave attributes 1
PERI_MS_PPU_FX535_SL_ATT2	0x40028DD8	FULL	Slave attributes 2
PERI_MS_PPU_FX535_SL_ATT3	0x40028DDC	FULL	Slave attributes 3
PERI_MS_PPU_FX535_MS_ADDR	0x40028DE0	FULL	Master region, base address
PERI_MS_PPU_FX535_MS_SIZE	0x40028DE4	FULL	Master region, size
PERI_MS_PPU_FX535_MS_ATT0	0x40028DF0	FULL	Master attributes 0
PERI_MS_PPU_FX535_MS_ATT1	0x40028DF4	FULL	Master attributes 1
PERI_MS_PPU_FX535_MS_ATT2	0x40028DF8	FULL	Master attributes 2
PERI_MS_PPU_FX535_MS_ATT3	0x40028DFC	FULL	Master attributes 3

21.553 PPU_FX 536

Register Name	Address	Permission	Description
PERI_MS_PPU_FX536_SL_ADDR	0x40028E00	FULL	Slave region, base address
PERI_MS_PPU_FX536_SL_SIZE	0x40028E04	FULL	Slave region, size
PERI_MS_PPU_FX536_SL_ATT0	0x40028E10	FULL	Slave attributes 0
PERI_MS_PPU_FX536_SL_ATT1	0x40028E14	FULL	Slave attributes 1
PERI_MS_PPU_FX536_SL_ATT2	0x40028E18	FULL	Slave attributes 2
PERI_MS_PPU_FX536_SL_ATT3	0x40028E1C	FULL	Slave attributes 3
PERI_MS_PPU_FX536_MS_ADDR	0x40028E20	FULL	Master region, base address
PERI_MS_PPU_FX536_MS_SIZE	0x40028E24	FULL	Master region, size
PERI_MS_PPU_FX536_MS_ATT0	0x40028E30	FULL	Master attributes 0
PERI_MS_PPU_FX536_MS_ATT1	0x40028E34	FULL	Master attributes 1
PERI_MS_PPU_FX536_MS_ATT2	0x40028E38	FULL	Master attributes 2
PERI_MS_PPU_FX536_MS_ATT3	0x40028E3C	FULL	Master attributes 3

21.554 PPU_FX 537

Register Name	Address	Permission	Description
PERI_MS_PPU_FX537_SL_ADDR	0x40028E40	FULL	Slave region, base address
PERI_MS_PPU_FX537_SL_SIZE	0x40028E44	FULL	Slave region, size
PERI_MS_PPU_FX537_SL_ATT0	0x40028E50	FULL	Slave attributes 0
PERI_MS_PPU_FX537_SL_ATT1	0x40028E54	FULL	Slave attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX537_SL_ATT2	0x40028E58	FULL	Slave attributes 2
PERI_MS_PPU_FX537_SL_ATT3	0x40028E5C	FULL	Slave attributes 3
PERI_MS_PPU_FX537_MS_ADDR	0x40028E60	FULL	Master region, base address
PERI_MS_PPU_FX537_MS_SIZE	0x40028E64	FULL	Master region, size
PERI_MS_PPU_FX537_MS_ATT0	0x40028E70	FULL	Master attributes 0
PERI_MS_PPU_FX537_MS_ATT1	0x40028E74	FULL	Master attributes 1
PERI_MS_PPU_FX537_MS_ATT2	0x40028E78	FULL	Master attributes 2
PERI_MS_PPU_FX537_MS_ATT3	0x40028E7C	FULL	Master attributes 3

21.555 PPU_FX 538

Register Name	Address	Permission	Description
PERI_MS_PPU_FX538_SL_ADDR	0x40028E80	FULL	Slave region, base address
PERI_MS_PPU_FX538_SL_SIZE	0x40028E84	FULL	Slave region, size
PERI_MS_PPU_FX538_SL_ATT0	0x40028E90	FULL	Slave attributes 0
PERI_MS_PPU_FX538_SL_ATT1	0x40028E94	FULL	Slave attributes 1
PERI_MS_PPU_FX538_SL_ATT2	0x40028E98	FULL	Slave attributes 2
PERI_MS_PPU_FX538_SL_ATT3	0x40028E9C	FULL	Slave attributes 3
PERI_MS_PPU_FX538_MS_ADDR	0x40028EA0	FULL	Master region, base address
PERI_MS_PPU_FX538_MS_SIZE	0x40028EA4	FULL	Master region, size
PERI_MS_PPU_FX538_MS_ATT0	0x40028EB0	FULL	Master attributes 0
PERI_MS_PPU_FX538_MS_ATT1	0x40028EB4	FULL	Master attributes 1
PERI_MS_PPU_FX538_MS_ATT2	0x40028EB8	FULL	Master attributes 2
PERI_MS_PPU_FX538_MS_ATT3	0x40028EBC	FULL	Master attributes 3

21.556 PPU_FX 539

Register Name	Address	Permission	Description
PERI_MS_PPU_FX539_SL_ADDR	0x40028EC0	FULL	Slave region, base address
PERI_MS_PPU_FX539_SL_SIZE	0x40028EC4	FULL	Slave region, size
PERI_MS_PPU_FX539_SL_ATT0	0x40028ED0	FULL	Slave attributes 0
PERI_MS_PPU_FX539_SL_ATT1	0x40028ED4	FULL	Slave attributes 1
PERI_MS_PPU_FX539_SL_ATT2	0x40028ED8	FULL	Slave attributes 2
PERI_MS_PPU_FX539_SL_ATT3	0x40028EDC	FULL	Slave attributes 3
PERI_MS_PPU_FX539_MS_ADDR	0x40028EE0	FULL	Master region, base address
PERI_MS_PPU_FX539_MS_SIZE	0x40028EE4	FULL	Master region, size
PERI_MS_PPU_FX539_MS_ATT0	0x40028EF0	FULL	Master attributes 0
PERI_MS_PPU_FX539_MS_ATT1	0x40028EF4	FULL	Master attributes 1
PERI_MS_PPU_FX539_MS_ATT2	0x40028EF8	FULL	Master attributes 2
PERI_MS_PPU_FX539_MS_ATT3	0x40028EFC	FULL	Master attributes 3

21.557 PPU_FX 540

Register Name	Address	Permission	Description
PERI_MS_PPU_FX540_SL_ADDR	0x40028F00	FULL	Slave region, base address
PERI_MS_PPU_FX540_SL_SIZE	0x40028F04	FULL	Slave region, size
PERI_MS_PPU_FX540_SL_ATT0	0x40028F10	FULL	Slave attributes 0
PERI_MS_PPU_FX540_SL_ATT1	0x40028F14	FULL	Slave attributes 1
PERI_MS_PPU_FX540_SL_ATT2	0x40028F18	FULL	Slave attributes 2
PERI_MS_PPU_FX540_SL_ATT3	0x40028F1C	FULL	Slave attributes 3
PERI_MS_PPU_FX540_MS_ADDR	0x40028F20	FULL	Master region, base address
PERI_MS_PPU_FX540_MS_SIZE	0x40028F24	FULL	Master region, size
PERI_MS_PPU_FX540_MS_ATT0	0x40028F30	FULL	Master attributes 0
PERI_MS_PPU_FX540_MS_ATT1	0x40028F34	FULL	Master attributes 1
PERI_MS_PPU_FX540_MS_ATT2	0x40028F38	FULL	Master attributes 2
PERI_MS_PPU_FX540_MS_ATT3	0x40028F3C	FULL	Master attributes 3

21.558 PPU_FX 541

Register Name	Address	Permission	Description
PERI_MS_PPU_FX541_SL_ADDR	0x40028F40	FULL	Slave region, base address
PERI_MS_PPU_FX541_SL_SIZE	0x40028F44	FULL	Slave region, size
PERI_MS_PPU_FX541_SL_ATT0	0x40028F50	FULL	Slave attributes 0
PERI_MS_PPU_FX541_SL_ATT1	0x40028F54	FULL	Slave attributes 1
PERI_MS_PPU_FX541_SL_ATT2	0x40028F58	FULL	Slave attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX541_SL_ATT3	0x40028F5C	FULL	Slave attributes 3
PERI_MS_PPU_FX541_MS_ADDR	0x40028F60	FULL	Master region, base address
PERI_MS_PPU_FX541_MS_SIZE	0x40028F64	FULL	Master region, size
PERI_MS_PPU_FX541_MS_ATT0	0x40028F70	FULL	Master attributes 0
PERI_MS_PPU_FX541_MS_ATT1	0x40028F74	FULL	Master attributes 1
PERI_MS_PPU_FX541_MS_ATT2	0x40028F78	FULL	Master attributes 2
PERI_MS_PPU_FX541_MS_ATT3	0x40028F7C	FULL	Master attributes 3

21.559 PPU_FX 542

Register Name	Address	Permission	Description
PERI_MS_PPU_FX542_SL_ADDR	0x40028F80	FULL	Slave region, base address
PERI_MS_PPU_FX542_SL_SIZE	0x40028F84	FULL	Slave region, size
PERI_MS_PPU_FX542_SL_ATT0	0x40028F90	FULL	Slave attributes 0
PERI_MS_PPU_FX542_SL_ATT1	0x40028F94	FULL	Slave attributes 1
PERI_MS_PPU_FX542_SL_ATT2	0x40028F98	FULL	Slave attributes 2
PERI_MS_PPU_FX542_SL_ATT3	0x40028F9C	FULL	Slave attributes 3
PERI_MS_PPU_FX542_MS_ADDR	0x40028FA0	FULL	Master region, base address
PERI_MS_PPU_FX542_MS_SIZE	0x40028FA4	FULL	Master region, size
PERI_MS_PPU_FX542_MS_ATT0	0x40028FB0	FULL	Master attributes 0
PERI_MS_PPU_FX542_MS_ATT1	0x40028FB4	FULL	Master attributes 1
PERI_MS_PPU_FX542_MS_ATT2	0x40028FB8	FULL	Master attributes 2
PERI_MS_PPU_FX542_MS_ATT3	0x40028FBC	FULL	Master attributes 3

21.560 PPU_FX 543

Register Name	Address	Permission	Description
PERI_MS_PPU_FX543_SL_ADDR	0x40028FC0	FULL	Slave region, base address
PERI_MS_PPU_FX543_SL_SIZE	0x40028FC4	FULL	Slave region, size
PERI_MS_PPU_FX543_SL_ATT0	0x40028FD0	FULL	Slave attributes 0
PERI_MS_PPU_FX543_SL_ATT1	0x40028FD4	FULL	Slave attributes 1
PERI_MS_PPU_FX543_SL_ATT2	0x40028FD8	FULL	Slave attributes 2
PERI_MS_PPU_FX543_SL_ATT3	0x40028FDC	FULL	Slave attributes 3
PERI_MS_PPU_FX543_MS_ADDR	0x40028FE0	FULL	Master region, base address
PERI_MS_PPU_FX543_MS_SIZE	0x40028FE4	FULL	Master region, size
PERI_MS_PPU_FX543_MS_ATT0	0x40028FF0	FULL	Master attributes 0
PERI_MS_PPU_FX543_MS_ATT1	0x40028FF4	FULL	Master attributes 1
PERI_MS_PPU_FX543_MS_ATT2	0x40028FF8	FULL	Master attributes 2
PERI_MS_PPU_FX543_MS_ATT3	0x40028FFC	FULL	Master attributes 3

21.561 PPU_FX 544

Register Name	Address	Permission	Description
PERI_MS_PPU_FX544_SL_ADDR	0x40029000	FULL	Slave region, base address
PERI_MS_PPU_FX544_SL_SIZE	0x40029004	FULL	Slave region, size
PERI_MS_PPU_FX544_SL_ATT0	0x40029010	FULL	Slave attributes 0
PERI_MS_PPU_FX544_SL_ATT1	0x40029014	FULL	Slave attributes 1
PERI_MS_PPU_FX544_SL_ATT2	0x40029018	FULL	Slave attributes 2
PERI_MS_PPU_FX544_SL_ATT3	0x4002901C	FULL	Slave attributes 3
PERI_MS_PPU_FX544_MS_ADDR	0x40029020	FULL	Master region, base address
PERI_MS_PPU_FX544_MS_SIZE	0x40029024	FULL	Master region, size
PERI_MS_PPU_FX544_MS_ATT0	0x40029030	FULL	Master attributes 0
PERI_MS_PPU_FX544_MS_ATT1	0x40029034	FULL	Master attributes 1
PERI_MS_PPU_FX544_MS_ATT2	0x40029038	FULL	Master attributes 2
PERI_MS_PPU_FX544_MS_ATT3	0x4002903C	FULL	Master attributes 3

21.562 PPU_FX 545

Register Name	Address	Permission	Description
PERI_MS_PPU_FX545_SL_ADDR	0x40029040	FULL	Slave region, base address
PERI_MS_PPU_FX545_SL_SIZE	0x40029044	FULL	Slave region, size
PERI_MS_PPU_FX545_SL_ATT0	0x40029050	FULL	Slave attributes 0
PERI_MS_PPU_FX545_SL_ATT1	0x40029054	FULL	Slave attributes 1
PERI_MS_PPU_FX545_SL_ATT2	0x40029058	FULL	Slave attributes 2
PERI_MS_PPU_FX545_SL_ATT3	0x4002905C	FULL	Slave attributes 3

Register Name	Address	Permission	Description
PERI_MS_PPU_FX545_MS_ADDR	0x40029060	FULL	Master region, base address
PERI_MS_PPU_FX545_MS_SIZE	0x40029064	FULL	Master region, size
PERI_MS_PPU_FX545_MS_ATT0	0x40029070	FULL	Master attributes 0
PERI_MS_PPU_FX545_MS_ATT1	0x40029074	FULL	Master attributes 1
PERI_MS_PPU_FX545_MS_ATT2	0x40029078	FULL	Master attributes 2
PERI_MS_PPU_FX545_MS_ATT3	0x4002907C	FULL	Master attributes 3

21.563 PPU_FX 546

Register Name	Address	Permission	Description
PERI_MS_PPU_FX546_SL_ADDR	0x40029080	FULL	Slave region, base address
PERI_MS_PPU_FX546_SL_SIZE	0x40029084	FULL	Slave region, size
PERI_MS_PPU_FX546_SL_ATT0	0x40029090	FULL	Slave attributes 0
PERI_MS_PPU_FX546_SL_ATT1	0x40029094	FULL	Slave attributes 1
PERI_MS_PPU_FX546_SL_ATT2	0x40029098	FULL	Slave attributes 2
PERI_MS_PPU_FX546_SL_ATT3	0x4002909C	FULL	Slave attributes 3
PERI_MS_PPU_FX546_MS_ADDR	0x400290A0	FULL	Master region, base address
PERI_MS_PPU_FX546_MS_SIZE	0x400290A4	FULL	Master region, size
PERI_MS_PPU_FX546_MS_ATT0	0x400290B0	FULL	Master attributes 0
PERI_MS_PPU_FX546_MS_ATT1	0x400290B4	FULL	Master attributes 1
PERI_MS_PPU_FX546_MS_ATT2	0x400290B8	FULL	Master attributes 2
PERI_MS_PPU_FX546_MS_ATT3	0x400290BC	FULL	Master attributes 3

21.564 PPU_FX 547

Register Name	Address	Permission	Description
PERI_MS_PPU_FX547_SL_ADDR	0x400290C0	FULL	Slave region, base address
PERI_MS_PPU_FX547_SL_SIZE	0x400290C4	FULL	Slave region, size
PERI_MS_PPU_FX547_SL_ATT0	0x400290D0	FULL	Slave attributes 0
PERI_MS_PPU_FX547_SL_ATT1	0x400290D4	FULL	Slave attributes 1
PERI_MS_PPU_FX547_SL_ATT2	0x400290D8	FULL	Slave attributes 2
PERI_MS_PPU_FX547_SL_ATT3	0x400290DC	FULL	Slave attributes 3
PERI_MS_PPU_FX547_MS_ADDR	0x400290E0	FULL	Master region, base address
PERI_MS_PPU_FX547_MS_SIZE	0x400290E4	FULL	Master region, size
PERI_MS_PPU_FX547_MS_ATT0	0x400290F0	FULL	Master attributes 0
PERI_MS_PPU_FX547_MS_ATT1	0x400290F4	FULL	Master attributes 1
PERI_MS_PPU_FX547_MS_ATT2	0x400290F8	FULL	Master attributes 2
PERI_MS_PPU_FX547_MS_ATT3	0x400290FC	FULL	Master attributes 3

21.565 PPU_FX 548

Register Name	Address	Permission	Description
PERI_MS_PPU_FX548_SL_ADDR	0x40029100	FULL	Slave region, base address
PERI_MS_PPU_FX548_SL_SIZE	0x40029104	FULL	Slave region, size
PERI_MS_PPU_FX548_SL_ATT0	0x40029110	FULL	Slave attributes 0
PERI_MS_PPU_FX548_SL_ATT1	0x40029114	FULL	Slave attributes 1
PERI_MS_PPU_FX548_SL_ATT2	0x40029118	FULL	Slave attributes 2
PERI_MS_PPU_FX548_SL_ATT3	0x4002911C	FULL	Slave attributes 3
PERI_MS_PPU_FX548_MS_ADDR	0x40029120	FULL	Master region, base address
PERI_MS_PPU_FX548_MS_SIZE	0x40029124	FULL	Master region, size
PERI_MS_PPU_FX548_MS_ATT0	0x40029130	FULL	Master attributes 0
PERI_MS_PPU_FX548_MS_ATT1	0x40029134	FULL	Master attributes 1
PERI_MS_PPU_FX548_MS_ATT2	0x40029138	FULL	Master attributes 2
PERI_MS_PPU_FX548_MS_ATT3	0x4002913C	FULL	Master attributes 3

21.566 PPU_FX 549

Register Name	Address	Permission	Description
PERI_MS_PPU_FX549_SL_ADDR	0x40029140	FULL	Slave region, base address
PERI_MS_PPU_FX549_SL_SIZE	0x40029144	FULL	Slave region, size
PERI_MS_PPU_FX549_SL_ATT0	0x40029150	FULL	Slave attributes 0
PERI_MS_PPU_FX549_SL_ATT1	0x40029154	FULL	Slave attributes 1
PERI_MS_PPU_FX549_SL_ATT2	0x40029158	FULL	Slave attributes 2
PERI_MS_PPU_FX549_SL_ATT3	0x4002915C	FULL	Slave attributes 3
PERI_MS_PPU_FX549_MS_ADDR	0x40029160	FULL	Master region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX549_MS_SIZE	0x40029164	FULL	Master region, size
PERI_MS_PPU_FX549_MS_ATT0	0x40029170	FULL	Master attributes 0
PERI_MS_PPU_FX549_MS_ATT1	0x40029174	FULL	Master attributes 1
PERI_MS_PPU_FX549_MS_ATT2	0x40029178	FULL	Master attributes 2
PERI_MS_PPU_FX549_MS_ATT3	0x4002917C	FULL	Master attributes 3

21.567 PPU_FX 550

Register Name	Address	Permission	Description
PERI_MS_PPU_FX550_SL_ADDR	0x40029180	FULL	Slave region, base address
PERI_MS_PPU_FX550_SL_SIZE	0x40029184	FULL	Slave region, size
PERI_MS_PPU_FX550_SL_ATT0	0x40029190	FULL	Slave attributes 0
PERI_MS_PPU_FX550_SL_ATT1	0x40029194	FULL	Slave attributes 1
PERI_MS_PPU_FX550_SL_ATT2	0x40029198	FULL	Slave attributes 2
PERI_MS_PPU_FX550_SL_ATT3	0x4002919C	FULL	Slave attributes 3
PERI_MS_PPU_FX550_MS_ADDR	0x400291A0	FULL	Master region, base address
PERI_MS_PPU_FX550_MS_SIZE	0x400291A4	FULL	Master region, size
PERI_MS_PPU_FX550_MS_ATT0	0x400291B0	FULL	Master attributes 0
PERI_MS_PPU_FX550_MS_ATT1	0x400291B4	FULL	Master attributes 1
PERI_MS_PPU_FX550_MS_ATT2	0x400291B8	FULL	Master attributes 2
PERI_MS_PPU_FX550_MS_ATT3	0x400291BC	FULL	Master attributes 3

21.568 PPU_FX 551

Register Name	Address	Permission	Description
PERI_MS_PPU_FX551_SL_ADDR	0x400291C0	FULL	Slave region, base address
PERI_MS_PPU_FX551_SL_SIZE	0x400291C4	FULL	Slave region, size
PERI_MS_PPU_FX551_SL_ATT0	0x400291D0	FULL	Slave attributes 0
PERI_MS_PPU_FX551_SL_ATT1	0x400291D4	FULL	Slave attributes 1
PERI_MS_PPU_FX551_SL_ATT2	0x400291D8	FULL	Slave attributes 2
PERI_MS_PPU_FX551_SL_ATT3	0x400291DC	FULL	Slave attributes 3
PERI_MS_PPU_FX551_MS_ADDR	0x400291E0	FULL	Master region, base address
PERI_MS_PPU_FX551_MS_SIZE	0x400291E4	FULL	Master region, size
PERI_MS_PPU_FX551_MS_ATT0	0x400291F0	FULL	Master attributes 0
PERI_MS_PPU_FX551_MS_ATT1	0x400291F4	FULL	Master attributes 1
PERI_MS_PPU_FX551_MS_ATT2	0x400291F8	FULL	Master attributes 2
PERI_MS_PPU_FX551_MS_ATT3	0x400291FC	FULL	Master attributes 3

21.569 PPU_FX 552

Register Name	Address	Permission	Description
PERI_MS_PPU_FX552_SL_ADDR	0x40029200	FULL	Slave region, base address
PERI_MS_PPU_FX552_SL_SIZE	0x40029204	FULL	Slave region, size
PERI_MS_PPU_FX552_SL_ATT0	0x40029210	FULL	Slave attributes 0
PERI_MS_PPU_FX552_SL_ATT1	0x40029214	FULL	Slave attributes 1
PERI_MS_PPU_FX552_SL_ATT2	0x40029218	FULL	Slave attributes 2
PERI_MS_PPU_FX552_SL_ATT3	0x4002921C	FULL	Slave attributes 3
PERI_MS_PPU_FX552_MS_ADDR	0x40029220	FULL	Master region, base address
PERI_MS_PPU_FX552_MS_SIZE	0x40029224	FULL	Master region, size
PERI_MS_PPU_FX552_MS_ATT0	0x40029230	FULL	Master attributes 0
PERI_MS_PPU_FX552_MS_ATT1	0x40029234	FULL	Master attributes 1
PERI_MS_PPU_FX552_MS_ATT2	0x40029238	FULL	Master attributes 2
PERI_MS_PPU_FX552_MS_ATT3	0x4002923C	FULL	Master attributes 3

21.570 PPU_FX 553

Register Name	Address	Permission	Description
PERI_MS_PPU_FX553_SL_ADDR	0x40029240	FULL	Slave region, base address
PERI_MS_PPU_FX553_SL_SIZE	0x40029244	FULL	Slave region, size
PERI_MS_PPU_FX553_SL_ATT0	0x40029250	FULL	Slave attributes 0
PERI_MS_PPU_FX553_SL_ATT1	0x40029254	FULL	Slave attributes 1
PERI_MS_PPU_FX553_SL_ATT2	0x40029258	FULL	Slave attributes 2
PERI_MS_PPU_FX553_SL_ATT3	0x4002925C	FULL	Slave attributes 3
PERI_MS_PPU_FX553_MS_ADDR	0x40029260	FULL	Master region, base address
PERI_MS_PPU_FX553_MS_SIZE	0x40029264	FULL	Master region, size

Register Name	Address	Permission	Description
PERI_MS_PPU_FX553_MS_ATT0	0x40029270	FULL	Master attributes 0
PERI_MS_PPU_FX553_MS_ATT1	0x40029274	FULL	Master attributes 1
PERI_MS_PPU_FX553_MS_ATT2	0x40029278	FULL	Master attributes 2
PERI_MS_PPU_FX553_MS_ATT3	0x4002927C	FULL	Master attributes 3

21.571 PPU_FX 554

Register Name	Address	Permission	Description
PERI_MS_PPU_FX554_SL_ADDR	0x40029280	FULL	Slave region, base address
PERI_MS_PPU_FX554_SL_SIZE	0x40029284	FULL	Slave region, size
PERI_MS_PPU_FX554_SL_ATT0	0x40029290	FULL	Slave attributes 0
PERI_MS_PPU_FX554_SL_ATT1	0x40029294	FULL	Slave attributes 1
PERI_MS_PPU_FX554_SL_ATT2	0x40029298	FULL	Slave attributes 2
PERI_MS_PPU_FX554_SL_ATT3	0x4002929C	FULL	Slave attributes 3
PERI_MS_PPU_FX554_MS_ADDR	0x400292A0	FULL	Master region, base address
PERI_MS_PPU_FX554_MS_SIZE	0x400292A4	FULL	Master region, size
PERI_MS_PPU_FX554_MS_ATT0	0x400292B0	FULL	Master attributes 0
PERI_MS_PPU_FX554_MS_ATT1	0x400292B4	FULL	Master attributes 1
PERI_MS_PPU_FX554_MS_ATT2	0x400292B8	FULL	Master attributes 2
PERI_MS_PPU_FX554_MS_ATT3	0x400292BC	FULL	Master attributes 3

21.572 PPU_FX 555

Register Name	Address	Permission	Description
PERI_MS_PPU_FX555_SL_ADDR	0x400292C0	FULL	Slave region, base address
PERI_MS_PPU_FX555_SL_SIZE	0x400292C4	FULL	Slave region, size
PERI_MS_PPU_FX555_SL_ATT0	0x400292D0	FULL	Slave attributes 0
PERI_MS_PPU_FX555_SL_ATT1	0x400292D4	FULL	Slave attributes 1
PERI_MS_PPU_FX555_SL_ATT2	0x400292D8	FULL	Slave attributes 2
PERI_MS_PPU_FX555_SL_ATT3	0x400292DC	FULL	Slave attributes 3
PERI_MS_PPU_FX555_MS_ADDR	0x400292E0	FULL	Master region, base address
PERI_MS_PPU_FX555_MS_SIZE	0x400292E4	FULL	Master region, size
PERI_MS_PPU_FX555_MS_ATT0	0x400292F0	FULL	Master attributes 0
PERI_MS_PPU_FX555_MS_ATT1	0x400292F4	FULL	Master attributes 1
PERI_MS_PPU_FX555_MS_ATT2	0x400292F8	FULL	Master attributes 2
PERI_MS_PPU_FX555_MS_ATT3	0x400292FC	FULL	Master attributes 3

21.573 PPU_FX 556

Register Name	Address	Permission	Description
PERI_MS_PPU_FX556_SL_ADDR	0x40029300	FULL	Slave region, base address
PERI_MS_PPU_FX556_SL_SIZE	0x40029304	FULL	Slave region, size
PERI_MS_PPU_FX556_SL_ATT0	0x40029310	FULL	Slave attributes 0
PERI_MS_PPU_FX556_SL_ATT1	0x40029314	FULL	Slave attributes 1
PERI_MS_PPU_FX556_SL_ATT2	0x40029318	FULL	Slave attributes 2
PERI_MS_PPU_FX556_SL_ATT3	0x4002931C	FULL	Slave attributes 3
PERI_MS_PPU_FX556_MS_ADDR	0x40029320	FULL	Master region, base address
PERI_MS_PPU_FX556_MS_SIZE	0x40029324	FULL	Master region, size
PERI_MS_PPU_FX556_MS_ATT0	0x40029330	FULL	Master attributes 0
PERI_MS_PPU_FX556_MS_ATT1	0x40029334	FULL	Master attributes 1
PERI_MS_PPU_FX556_MS_ATT2	0x40029338	FULL	Master attributes 2
PERI_MS_PPU_FX556_MS_ATT3	0x4002933C	FULL	Master attributes 3

21.574 PPU_FX 557

Register Name	Address	Permission	Description
PERI_MS_PPU_FX557_SL_ADDR	0x40029340	FULL	Slave region, base address
PERI_MS_PPU_FX557_SL_SIZE	0x40029344	FULL	Slave region, size
PERI_MS_PPU_FX557_SL_ATT0	0x40029350	FULL	Slave attributes 0
PERI_MS_PPU_FX557_SL_ATT1	0x40029354	FULL	Slave attributes 1
PERI_MS_PPU_FX557_SL_ATT2	0x40029358	FULL	Slave attributes 2
PERI_MS_PPU_FX557_SL_ATT3	0x4002935C	FULL	Slave attributes 3
PERI_MS_PPU_FX557_MS_ADDR	0x40029360	FULL	Master region, base address
PERI_MS_PPU_FX557_MS_SIZE	0x40029364	FULL	Master region, size
PERI_MS_PPU_FX557_MS_ATT0	0x40029370	FULL	Master attributes 0

Register Name	Address	Permission	Description
PERI_MS_PPU_FX557_MS_ATT1	0x40029374	FULL	Master attributes 1
PERI_MS_PPU_FX557_MS_ATT2	0x40029378	FULL	Master attributes 2
PERI_MS_PPU_FX557_MS_ATT3	0x4002937C	FULL	Master attributes 3

21.575 PPU_FX 558

Register Name	Address	Permission	Description
PERI_MS_PPU_FX558_SL_ADDR	0x40029380	FULL	Slave region, base address
PERI_MS_PPU_FX558_SL_SIZE	0x40029384	FULL	Slave region, size
PERI_MS_PPU_FX558_SL_ATT0	0x40029390	FULL	Slave attributes 0
PERI_MS_PPU_FX558_SL_ATT1	0x40029394	FULL	Slave attributes 1
PERI_MS_PPU_FX558_SL_ATT2	0x40029398	FULL	Slave attributes 2
PERI_MS_PPU_FX558_SL_ATT3	0x4002939C	FULL	Slave attributes 3
PERI_MS_PPU_FX558_MS_ADDR	0x400293A0	FULL	Master region, base address
PERI_MS_PPU_FX558_MS_SIZE	0x400293A4	FULL	Master region, size
PERI_MS_PPU_FX558_MS_ATT0	0x400293B0	FULL	Master attributes 0
PERI_MS_PPU_FX558_MS_ATT1	0x400293B4	FULL	Master attributes 1
PERI_MS_PPU_FX558_MS_ATT2	0x400293B8	FULL	Master attributes 2
PERI_MS_PPU_FX558_MS_ATT3	0x400293BC	FULL	Master attributes 3

21.576 PPU_FX 559

Register Name	Address	Permission	Description
PERI_MS_PPU_FX559_SL_ADDR	0x400293C0	FULL	Slave region, base address
PERI_MS_PPU_FX559_SL_SIZE	0x400293C4	FULL	Slave region, size
PERI_MS_PPU_FX559_SL_ATT0	0x400293D0	FULL	Slave attributes 0
PERI_MS_PPU_FX559_SL_ATT1	0x400293D4	FULL	Slave attributes 1
PERI_MS_PPU_FX559_SL_ATT2	0x400293D8	FULL	Slave attributes 2
PERI_MS_PPU_FX559_SL_ATT3	0x400293DC	FULL	Slave attributes 3
PERI_MS_PPU_FX559_MS_ADDR	0x400293E0	FULL	Master region, base address
PERI_MS_PPU_FX559_MS_SIZE	0x400293E4	FULL	Master region, size
PERI_MS_PPU_FX559_MS_ATT0	0x400293F0	FULL	Master attributes 0
PERI_MS_PPU_FX559_MS_ATT1	0x400293F4	FULL	Master attributes 1
PERI_MS_PPU_FX559_MS_ATT2	0x400293F8	FULL	Master attributes 2
PERI_MS_PPU_FX559_MS_ATT3	0x400293FC	FULL	Master attributes 3

21.577 PPU_FX 560

Register Name	Address	Permission	Description
PERI_MS_PPU_FX560_SL_ADDR	0x40029400	FULL	Slave region, base address
PERI_MS_PPU_FX560_SL_SIZE	0x40029404	FULL	Slave region, size
PERI_MS_PPU_FX560_SL_ATT0	0x40029410	FULL	Slave attributes 0
PERI_MS_PPU_FX560_SL_ATT1	0x40029414	FULL	Slave attributes 1
PERI_MS_PPU_FX560_SL_ATT2	0x40029418	FULL	Slave attributes 2
PERI_MS_PPU_FX560_SL_ATT3	0x4002941C	FULL	Slave attributes 3
PERI_MS_PPU_FX560_MS_ADDR	0x40029420	FULL	Master region, base address
PERI_MS_PPU_FX560_MS_SIZE	0x40029424	FULL	Master region, size
PERI_MS_PPU_FX560_MS_ATT0	0x40029430	FULL	Master attributes 0
PERI_MS_PPU_FX560_MS_ATT1	0x40029434	FULL	Master attributes 1
PERI_MS_PPU_FX560_MS_ATT2	0x40029438	FULL	Master attributes 2
PERI_MS_PPU_FX560_MS_ATT3	0x4002943C	FULL	Master attributes 3

21.578 PPU_FX 561

Register Name	Address	Permission	Description
PERI_MS_PPU_FX561_SL_ADDR	0x40029440	FULL	Slave region, base address
PERI_MS_PPU_FX561_SL_SIZE	0x40029444	FULL	Slave region, size
PERI_MS_PPU_FX561_SL_ATT0	0x40029450	FULL	Slave attributes 0
PERI_MS_PPU_FX561_SL_ATT1	0x40029454	FULL	Slave attributes 1
PERI_MS_PPU_FX561_SL_ATT2	0x40029458	FULL	Slave attributes 2
PERI_MS_PPU_FX561_SL_ATT3	0x4002945C	FULL	Slave attributes 3
PERI_MS_PPU_FX561_MS_ADDR	0x40029460	FULL	Master region, base address
PERI_MS_PPU_FX561_MS_SIZE	0x40029464	FULL	Master region, size
PERI_MS_PPU_FX561_MS_ATT0	0x40029470	FULL	Master attributes 0
PERI_MS_PPU_FX561_MS_ATT1	0x40029474	FULL	Master attributes 1

Register Name	Address	Permission	Description
PERI_MS_PPU_FX561_MS_ATT2	0x40029478	FULL	Master attributes 2
PERI_MS_PPU_FX561_MS_ATT3	0x4002947C	FULL	Master attributes 3

21.579 PPU_FX 562

Register Name	Address	Permission	Description
PERI_MS_PPU_FX562_SL_ADDR	0x40029480	FULL	Slave region, base address
PERI_MS_PPU_FX562_SL_SIZE	0x40029484	FULL	Slave region, size
PERI_MS_PPU_FX562_SL_ATT0	0x40029490	FULL	Slave attributes 0
PERI_MS_PPU_FX562_SL_ATT1	0x40029494	FULL	Slave attributes 1
PERI_MS_PPU_FX562_SL_ATT2	0x40029498	FULL	Slave attributes 2
PERI_MS_PPU_FX562_SL_ATT3	0x4002949C	FULL	Slave attributes 3
PERI_MS_PPU_FX562_MS_ADDR	0x400294A0	FULL	Master region, base address
PERI_MS_PPU_FX562_MS_SIZE	0x400294A4	FULL	Master region, size
PERI_MS_PPU_FX562_MS_ATT0	0x400294B0	FULL	Master attributes 0
PERI_MS_PPU_FX562_MS_ATT1	0x400294B4	FULL	Master attributes 1
PERI_MS_PPU_FX562_MS_ATT2	0x400294B8	FULL	Master attributes 2
PERI_MS_PPU_FX562_MS_ATT3	0x400294BC	FULL	Master attributes 3

21.580 PPU_FX 563

Register Name	Address	Permission	Description
PERI_MS_PPU_FX563_SL_ADDR	0x400294C0	FULL	Slave region, base address
PERI_MS_PPU_FX563_SL_SIZE	0x400294C4	FULL	Slave region, size
PERI_MS_PPU_FX563_SL_ATT0	0x400294D0	FULL	Slave attributes 0
PERI_MS_PPU_FX563_SL_ATT1	0x400294D4	FULL	Slave attributes 1
PERI_MS_PPU_FX563_SL_ATT2	0x400294D8	FULL	Slave attributes 2
PERI_MS_PPU_FX563_SL_ATT3	0x400294DC	FULL	Slave attributes 3
PERI_MS_PPU_FX563_MS_ADDR	0x400294E0	FULL	Master region, base address
PERI_MS_PPU_FX563_MS_SIZE	0x400294E4	FULL	Master region, size
PERI_MS_PPU_FX563_MS_ATT0	0x400294F0	FULL	Master attributes 0
PERI_MS_PPU_FX563_MS_ATT1	0x400294F4	FULL	Master attributes 1
PERI_MS_PPU_FX563_MS_ATT2	0x400294F8	FULL	Master attributes 2
PERI_MS_PPU_FX563_MS_ATT3	0x400294FC	FULL	Master attributes 3

21.581 PPU_FX 564

Register Name	Address	Permission	Description
PERI_MS_PPU_FX564_SL_ADDR	0x40029500	FULL	Slave region, base address
PERI_MS_PPU_FX564_SL_SIZE	0x40029504	FULL	Slave region, size
PERI_MS_PPU_FX564_SL_ATT0	0x40029510	FULL	Slave attributes 0
PERI_MS_PPU_FX564_SL_ATT1	0x40029514	FULL	Slave attributes 1
PERI_MS_PPU_FX564_SL_ATT2	0x40029518	FULL	Slave attributes 2
PERI_MS_PPU_FX564_SL_ATT3	0x4002951C	FULL	Slave attributes 3
PERI_MS_PPU_FX564_MS_ADDR	0x40029520	FULL	Master region, base address
PERI_MS_PPU_FX564_MS_SIZE	0x40029524	FULL	Master region, size
PERI_MS_PPU_FX564_MS_ATT0	0x40029530	FULL	Master attributes 0
PERI_MS_PPU_FX564_MS_ATT1	0x40029534	FULL	Master attributes 1
PERI_MS_PPU_FX564_MS_ATT2	0x40029538	FULL	Master attributes 2
PERI_MS_PPU_FX564_MS_ATT3	0x4002953C	FULL	Master attributes 3

21.582 PPU_FX 565

Register Name	Address	Permission	Description
PERI_MS_PPU_FX565_SL_ADDR	0x40029540	FULL	Slave region, base address
PERI_MS_PPU_FX565_SL_SIZE	0x40029544	FULL	Slave region, size
PERI_MS_PPU_FX565_SL_ATT0	0x40029550	FULL	Slave attributes 0
PERI_MS_PPU_FX565_SL_ATT1	0x40029554	FULL	Slave attributes 1
PERI_MS_PPU_FX565_SL_ATT2	0x40029558	FULL	Slave attributes 2
PERI_MS_PPU_FX565_SL_ATT3	0x4002955C	FULL	Slave attributes 3
PERI_MS_PPU_FX565_MS_ADDR	0x40029560	FULL	Master region, base address
PERI_MS_PPU_FX565_MS_SIZE	0x40029564	FULL	Master region, size
PERI_MS_PPU_FX565_MS_ATT0	0x40029570	FULL	Master attributes 0
PERI_MS_PPU_FX565_MS_ATT1	0x40029574	FULL	Master attributes 1
PERI_MS_PPU_FX565_MS_ATT2	0x40029578	FULL	Master attributes 2

Register Name	Address	Permission	Description
PERI_MS_PPU_FX565_MS_ATT3	0x4002957C	FULL	Master attributes 3

21.583 PPU_FX 566

Register Name	Address	Permission	Description
PERI_MS_PPU_FX566_SL_ADDR	0x40029580	FULL	Slave region, base address
PERI_MS_PPU_FX566_SL_SIZE	0x40029584	FULL	Slave region, size
PERI_MS_PPU_FX566_SL_ATT0	0x40029590	FULL	Slave attributes 0
PERI_MS_PPU_FX566_SL_ATT1	0x40029594	FULL	Slave attributes 1
PERI_MS_PPU_FX566_SL_ATT2	0x40029598	FULL	Slave attributes 2
PERI_MS_PPU_FX566_SL_ATT3	0x4002959C	FULL	Slave attributes 3
PERI_MS_PPU_FX566_MS_ADDR	0x400295A0	FULL	Master region, base address
PERI_MS_PPU_FX566_MS_SIZE	0x400295A4	FULL	Master region, size
PERI_MS_PPU_FX566_MS_ATT0	0x400295B0	FULL	Master attributes 0
PERI_MS_PPU_FX566_MS_ATT1	0x400295B4	FULL	Master attributes 1
PERI_MS_PPU_FX566_MS_ATT2	0x400295B8	FULL	Master attributes 2
PERI_MS_PPU_FX566_MS_ATT3	0x400295BC	FULL	Master attributes 3

21.584 PPU_FX 567

Register Name	Address	Permission	Description
PERI_MS_PPU_FX567_SL_ADDR	0x400295C0	FULL	Slave region, base address
PERI_MS_PPU_FX567_SL_SIZE	0x400295C4	FULL	Slave region, size
PERI_MS_PPU_FX567_SL_ATT0	0x400295D0	FULL	Slave attributes 0
PERI_MS_PPU_FX567_SL_ATT1	0x400295D4	FULL	Slave attributes 1
PERI_MS_PPU_FX567_SL_ATT2	0x400295D8	FULL	Slave attributes 2
PERI_MS_PPU_FX567_SL_ATT3	0x400295DC	FULL	Slave attributes 3
PERI_MS_PPU_FX567_MS_ADDR	0x400295E0	FULL	Master region, base address
PERI_MS_PPU_FX567_MS_SIZE	0x400295E4	FULL	Master region, size
PERI_MS_PPU_FX567_MS_ATT0	0x400295F0	FULL	Master attributes 0
PERI_MS_PPU_FX567_MS_ATT1	0x400295F4	FULL	Master attributes 1
PERI_MS_PPU_FX567_MS_ATT2	0x400295F8	FULL	Master attributes 2
PERI_MS_PPU_FX567_MS_ATT3	0x400295FC	FULL	Master attributes 3

21.585 PPU_FX 568

Register Name	Address	Permission	Description
PERI_MS_PPU_FX568_SL_ADDR	0x40029600	FULL	Slave region, base address
PERI_MS_PPU_FX568_SL_SIZE	0x40029604	FULL	Slave region, size
PERI_MS_PPU_FX568_SL_ATT0	0x40029610	FULL	Slave attributes 0
PERI_MS_PPU_FX568_SL_ATT1	0x40029614	FULL	Slave attributes 1
PERI_MS_PPU_FX568_SL_ATT2	0x40029618	FULL	Slave attributes 2
PERI_MS_PPU_FX568_SL_ATT3	0x4002961C	FULL	Slave attributes 3
PERI_MS_PPU_FX568_MS_ADDR	0x40029620	FULL	Master region, base address
PERI_MS_PPU_FX568_MS_SIZE	0x40029624	FULL	Master region, size
PERI_MS_PPU_FX568_MS_ATT0	0x40029630	FULL	Master attributes 0
PERI_MS_PPU_FX568_MS_ATT1	0x40029634	FULL	Master attributes 1
PERI_MS_PPU_FX568_MS_ATT2	0x40029638	FULL	Master attributes 2
PERI_MS_PPU_FX568_MS_ATT3	0x4002963C	FULL	Master attributes 3

21.586 PPU_FX 569

Register Name	Address	Permission	Description
PERI_MS_PPU_FX569_SL_ADDR	0x40029640	FULL	Slave region, base address
PERI_MS_PPU_FX569_SL_SIZE	0x40029644	FULL	Slave region, size
PERI_MS_PPU_FX569_SL_ATT0	0x40029650	FULL	Slave attributes 0
PERI_MS_PPU_FX569_SL_ATT1	0x40029654	FULL	Slave attributes 1
PERI_MS_PPU_FX569_SL_ATT2	0x40029658	FULL	Slave attributes 2
PERI_MS_PPU_FX569_SL_ATT3	0x4002965C	FULL	Slave attributes 3
PERI_MS_PPU_FX569_MS_ADDR	0x40029660	FULL	Master region, base address
PERI_MS_PPU_FX569_MS_SIZE	0x40029664	FULL	Master region, size
PERI_MS_PPU_FX569_MS_ATT0	0x40029670	FULL	Master attributes 0
PERI_MS_PPU_FX569_MS_ATT1	0x40029674	FULL	Master attributes 1
PERI_MS_PPU_FX569_MS_ATT2	0x40029678	FULL	Master attributes 2
PERI_MS_PPU_FX569_MS_ATT3	0x4002967C	FULL	Master attributes 3

21.587 PPU_FX 570

Register Name	Address	Permission	Description
PERI_MS_PPU_FX570_SL_ADDR	0x40029680	FULL	Slave region, base address
PERI_MS_PPU_FX570_SL_SIZE	0x40029684	FULL	Slave region, size
PERI_MS_PPU_FX570_SL_ATT0	0x40029690	FULL	Slave attributes 0
PERI_MS_PPU_FX570_SL_ATT1	0x40029694	FULL	Slave attributes 1
PERI_MS_PPU_FX570_SL_ATT2	0x40029698	FULL	Slave attributes 2
PERI_MS_PPU_FX570_SL_ATT3	0x4002969C	FULL	Slave attributes 3
PERI_MS_PPU_FX570_MS_ADDR	0x400296A0	FULL	Master region, base address
PERI_MS_PPU_FX570_MS_SIZE	0x400296A4	FULL	Master region, size
PERI_MS_PPU_FX570_MS_ATT0	0x400296B0	FULL	Master attributes 0
PERI_MS_PPU_FX570_MS_ATT1	0x400296B4	FULL	Master attributes 1
PERI_MS_PPU_FX570_MS_ATT2	0x400296B8	FULL	Master attributes 2
PERI_MS_PPU_FX570_MS_ATT3	0x400296BC	FULL	Master attributes 3

21.588 PPU_FX 571

Register Name	Address	Permission	Description
PERI_MS_PPU_FX571_SL_ADDR	0x400296C0	FULL	Slave region, base address
PERI_MS_PPU_FX571_SL_SIZE	0x400296C4	FULL	Slave region, size
PERI_MS_PPU_FX571_SL_ATT0	0x400296D0	FULL	Slave attributes 0
PERI_MS_PPU_FX571_SL_ATT1	0x400296D4	FULL	Slave attributes 1
PERI_MS_PPU_FX571_SL_ATT2	0x400296D8	FULL	Slave attributes 2
PERI_MS_PPU_FX571_SL_ATT3	0x400296DC	FULL	Slave attributes 3
PERI_MS_PPU_FX571_MS_ADDR	0x400296E0	FULL	Master region, base address
PERI_MS_PPU_FX571_MS_SIZE	0x400296E4	FULL	Master region, size
PERI_MS_PPU_FX571_MS_ATT0	0x400296F0	FULL	Master attributes 0
PERI_MS_PPU_FX571_MS_ATT1	0x400296F4	FULL	Master attributes 1
PERI_MS_PPU_FX571_MS_ATT2	0x400296F8	FULL	Master attributes 2
PERI_MS_PPU_FX571_MS_ATT3	0x400296FC	FULL	Master attributes 3

21.589 PPU_FX 572

Register Name	Address	Permission	Description
PERI_MS_PPU_FX572_SL_ADDR	0x40029700	FULL	Slave region, base address
PERI_MS_PPU_FX572_SL_SIZE	0x40029704	FULL	Slave region, size
PERI_MS_PPU_FX572_SL_ATT0	0x40029710	FULL	Slave attributes 0
PERI_MS_PPU_FX572_SL_ATT1	0x40029714	FULL	Slave attributes 1
PERI_MS_PPU_FX572_SL_ATT2	0x40029718	FULL	Slave attributes 2
PERI_MS_PPU_FX572_SL_ATT3	0x4002971C	FULL	Slave attributes 3
PERI_MS_PPU_FX572_MS_ADDR	0x40029720	FULL	Master region, base address
PERI_MS_PPU_FX572_MS_SIZE	0x40029724	FULL	Master region, size
PERI_MS_PPU_FX572_MS_ATT0	0x40029730	FULL	Master attributes 0
PERI_MS_PPU_FX572_MS_ATT1	0x40029734	FULL	Master attributes 1
PERI_MS_PPU_FX572_MS_ATT2	0x40029738	FULL	Master attributes 2
PERI_MS_PPU_FX572_MS_ATT3	0x4002973C	FULL	Master attributes 3

21.590 PPU_FX 573

Register Name	Address	Permission	Description
PERI_MS_PPU_FX573_SL_ADDR	0x40029740	FULL	Slave region, base address
PERI_MS_PPU_FX573_SL_SIZE	0x40029744	FULL	Slave region, size
PERI_MS_PPU_FX573_SL_ATT0	0x40029750	FULL	Slave attributes 0
PERI_MS_PPU_FX573_SL_ATT1	0x40029754	FULL	Slave attributes 1
PERI_MS_PPU_FX573_SL_ATT2	0x40029758	FULL	Slave attributes 2
PERI_MS_PPU_FX573_SL_ATT3	0x4002975C	FULL	Slave attributes 3
PERI_MS_PPU_FX573_MS_ADDR	0x40029760	FULL	Master region, base address
PERI_MS_PPU_FX573_MS_SIZE	0x40029764	FULL	Master region, size
PERI_MS_PPU_FX573_MS_ATT0	0x40029770	FULL	Master attributes 0
PERI_MS_PPU_FX573_MS_ATT1	0x40029774	FULL	Master attributes 1
PERI_MS_PPU_FX573_MS_ATT2	0x40029778	FULL	Master attributes 2
PERI_MS_PPU_FX573_MS_ATT3	0x4002977C	FULL	Master attributes 3

21.591 PPU_FX 574

Register Name	Address	Permission	Description
PERI_MS_PPU_FX574_SL_ADDR	0x40029780	FULL	Slave region, base address
PERI_MS_PPU_FX574_SL_SIZE	0x40029784	FULL	Slave region, size
PERI_MS_PPU_FX574_SL_ATT0	0x40029790	FULL	Slave attributes 0
PERI_MS_PPU_FX574_SL_ATT1	0x40029794	FULL	Slave attributes 1
PERI_MS_PPU_FX574_SL_ATT2	0x40029798	FULL	Slave attributes 2
PERI_MS_PPU_FX574_SL_ATT3	0x4002979C	FULL	Slave attributes 3
PERI_MS_PPU_FX574_MS_ADDR	0x400297A0	FULL	Master region, base address
PERI_MS_PPU_FX574_MS_SIZE	0x400297A4	FULL	Master region, size
PERI_MS_PPU_FX574_MS_ATT0	0x400297B0	FULL	Master attributes 0
PERI_MS_PPU_FX574_MS_ATT1	0x400297B4	FULL	Master attributes 1
PERI_MS_PPU_FX574_MS_ATT2	0x400297B8	FULL	Master attributes 2
PERI_MS_PPU_FX574_MS_ATT3	0x400297BC	FULL	Master attributes 3

21.592 PPU_FX 575

Register Name	Address	Permission	Description
PERI_MS_PPU_FX575_SL_ADDR	0x400297C0	FULL	Slave region, base address
PERI_MS_PPU_FX575_SL_SIZE	0x400297C4	FULL	Slave region, size
PERI_MS_PPU_FX575_SL_ATT0	0x400297D0	FULL	Slave attributes 0
PERI_MS_PPU_FX575_SL_ATT1	0x400297D4	FULL	Slave attributes 1
PERI_MS_PPU_FX575_SL_ATT2	0x400297D8	FULL	Slave attributes 2
PERI_MS_PPU_FX575_SL_ATT3	0x400297DC	FULL	Slave attributes 3
PERI_MS_PPU_FX575_MS_ADDR	0x400297E0	FULL	Master region, base address
PERI_MS_PPU_FX575_MS_SIZE	0x400297E4	FULL	Master region, size
PERI_MS_PPU_FX575_MS_ATT0	0x400297F0	FULL	Master attributes 0
PERI_MS_PPU_FX575_MS_ATT1	0x400297F4	FULL	Master attributes 1
PERI_MS_PPU_FX575_MS_ATT2	0x400297F8	FULL	Master attributes 2
PERI_MS_PPU_FX575_MS_ATT3	0x400297FC	FULL	Master attributes 3

21.593 PPU_FX 576

Register Name	Address	Permission	Description
PERI_MS_PPU_FX576_SL_ADDR	0x40029800	FULL	Slave region, base address
PERI_MS_PPU_FX576_SL_SIZE	0x40029804	FULL	Slave region, size
PERI_MS_PPU_FX576_SL_ATT0	0x40029810	FULL	Slave attributes 0
PERI_MS_PPU_FX576_SL_ATT1	0x40029814	FULL	Slave attributes 1
PERI_MS_PPU_FX576_SL_ATT2	0x40029818	FULL	Slave attributes 2
PERI_MS_PPU_FX576_SL_ATT3	0x4002981C	FULL	Slave attributes 3
PERI_MS_PPU_FX576_MS_ADDR	0x40029820	FULL	Master region, base address
PERI_MS_PPU_FX576_MS_SIZE	0x40029824	FULL	Master region, size
PERI_MS_PPU_FX576_MS_ATT0	0x40029830	FULL	Master attributes 0
PERI_MS_PPU_FX576_MS_ATT1	0x40029834	FULL	Master attributes 1
PERI_MS_PPU_FX576_MS_ATT2	0x40029838	FULL	Master attributes 2
PERI_MS_PPU_FX576_MS_ATT3	0x4002983C	FULL	Master attributes 3

21.594 PPU_FX 577

Register Name	Address	Permission	Description
PERI_MS_PPU_FX577_SL_ADDR	0x40029840	FULL	Slave region, base address
PERI_MS_PPU_FX577_SL_SIZE	0x40029844	FULL	Slave region, size
PERI_MS_PPU_FX577_SL_ATT0	0x40029850	FULL	Slave attributes 0
PERI_MS_PPU_FX577_SL_ATT1	0x40029854	FULL	Slave attributes 1
PERI_MS_PPU_FX577_SL_ATT2	0x40029858	FULL	Slave attributes 2
PERI_MS_PPU_FX577_SL_ATT3	0x4002985C	FULL	Slave attributes 3
PERI_MS_PPU_FX577_MS_ADDR	0x40029860	FULL	Master region, base address
PERI_MS_PPU_FX577_MS_SIZE	0x40029864	FULL	Master region, size
PERI_MS_PPU_FX577_MS_ATT0	0x40029870	FULL	Master attributes 0
PERI_MS_PPU_FX577_MS_ATT1	0x40029874	FULL	Master attributes 1
PERI_MS_PPU_FX577_MS_ATT2	0x40029878	FULL	Master attributes 2
PERI_MS_PPU_FX577_MS_ATT3	0x4002987C	FULL	Master attributes 3

21.595 PPU_FX 578

Register Name	Address	Permission	Description
PERI_MS_PPU_FX578_SL_ADDR	0x40029880	FULL	Slave region, base address

Register Name	Address	Permission	Description
PERI_MS_PPU_FX578_SL_SIZE	0x40029884	FULL	Slave region, size
PERI_MS_PPU_FX578_SL_ATT0	0x40029890	FULL	Slave attributes 0
PERI_MS_PPU_FX578_SL_ATT1	0x40029894	FULL	Slave attributes 1
PERI_MS_PPU_FX578_SL_ATT2	0x40029898	FULL	Slave attributes 2
PERI_MS_PPU_FX578_SL_ATT3	0x4002989C	FULL	Slave attributes 3
PERI_MS_PPU_FX578_MS_ADDR	0x400298A0	FULL	Master region, base address
PERI_MS_PPU_FX578_MS_SIZE	0x400298A4	FULL	Master region, size
PERI_MS_PPU_FX578_MS_ATT0	0x400298B0	FULL	Master attributes 0
PERI_MS_PPU_FX578_MS_ATT1	0x400298B4	FULL	Master attributes 1
PERI_MS_PPU_FX578_MS_ATT2	0x400298B8	FULL	Master attributes 2
PERI_MS_PPU_FX578_MS_ATT3	0x400298BC	FULL	Master attributes 3

21.596 Register Details

21.596.1 PPU_PR

21.596.1.1 PERI_MS_PPU_PR_SL_ADDR

Description: Slave region, base address

Address: 0x40020000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: SL_ADDR can only be written by protection context '0' (protection context '0' has unrestricted access). The access privileges for other protection contexts are determined by MS_ATT0, ..., MS_ATT3, with the additional restriction that SL_ADDR can NOT be written.

Typically, the SL_ADDR and SL_SIZE registers are programmed by the boot process with protection context '0'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	ADDR30 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR30 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR30 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	ADDR30	RW	RW	Undefined	This field specifies the base address of the slave region. The region size is defined by SL_SIZE.REGION_SIZE. A region of n Bytes must be n Byte aligned. Therefore, some of the lesser significant address bits of ADDR30 must be '0's. E.g., a 64 KB address region (REGION_SIZE is '15') must be 64 KByte aligned, and ADDR30[13:0] must be '0's.

21.596.1.2 PERI_MS_PPU_PR_SL_SIZE

Description: Slave region, size
Address: 0x40020004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: SL_SIZE can only be written by protection context '0' (protection context '0' has unrestricted access). The access privileges for other protection contexts are determined by MS_ATT0, ..., MS_ATT3, with the additional restriction that SL_SIZE can NOT be written.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:29]		REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
24:28	REGION_SIZE	RW	RW	Undefined	This field specifies the size of the slave region: '0': Undefined. '1': 4 B region (this is the smallest region size). '2': 8 B region '3': 16 B region '4': 32 B region '5': 64 B region '6': 128 B region '7': 256 B region '8': 512 B region '9': 1 KB region '10': 2 KB region '11': 4 KB region '12': 8 KB region '13': 16 KB region '14': 32 KB region '15': 64 KB region '16': 128 KB region '17': 256 KB region '18': 512 KB region '19': 1 MB region '20': 2 MB region '21': 4 MB region '22': 8 MB region '23': 16 MB region '24': 32 MB region '25': 64 MB region '26': 128 MB region '27': 256 MB region '28': 512 MB region '29': 1 GB region '30': 2 GB region '31': 4 GB region

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	RW	RW	0	Slave region enable: '0': Disabled. A disabled region will never result in a match on the transfer address. '1': Enabled.

21.596.1.3 PERI_MS_PPU_PR_SL_ATT0

Description: Slave attributes 0
Address: 0x40020010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: The access privileges for SL_ATT0, ..., SL_ATT3 are determined by MS_ATT0, ..., MS_ATT3.

Note that protection context '0' has unrestricted access: PC0_UR, ..., PC0_NS fields are fixed to '1's. The other protection contexts have SW programmable fields.

Typically, the SL_ATT0, ..., SL_ATT3 registers are initialized by the boot process with protection context '0'.

For 4 or less protection contexts (PC_NR ≤ 4), only SL_ATT0 is present. For 5 through 8 protection contexts, only SL_ATT0 and SL_ATT1 are present. For 9 through 12 or less protection contexts, only SL_ATT0, SL_ATT1 and SL_ATT2 are present. For 13 through 16 protection contexts, SL_ATT0, SL_ATT1, SL_ATT2 and SL_ATT3 are all present. If the number of protection contexts is not a multiple of 4, the 'missing' protection contexts in a register have no associated access fields (and the field positions read as '0').

Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC0_NS [4:4]	PC0_PW [3:3]	PC0_PR [2:2]	PC0_UW [1:1]	PC0_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC1_NS [12:12]	PC1_PW [11:11]	PC1_PR [10:10]	PC1_UW [9:9]	PC1_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC2_NS [20:20]	PC2_PW [19:19]	PC2_PR [18:18]	PC2_UW [17:17]	PC2_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC3_NS [28:28]	PC3_PW [27:27]	PC3_PR [26:26]	PC3_UW [25:25]	PC3_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC0_UR	R	R	1	Protection context 0, user read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	PC0_UW	R	R	1	Protection context 0, user write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	PC0_PR	R	R	1	Protection context 0, privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
3	PC0_PW	R	R	1	Protection context 0, privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).

Bits	Name	SW	HW	Default or Enum	Description
4	PC0_NS	R	R	1	Protection context 0, non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC1_UR	RW	RW	1	Protection context 1, user read enable.
9	PC1_UW	RW	RW	1	Protection context 1, user write enable.
10	PC1_PR	RW	RW	1	Protection context 1, privileged read enable.
11	PC1_PW	RW	RW	1	Protection context 1, privileged write enable.
12	PC1_NS	RW	RW	1	Protection context 1, non-secure.
16	PC2_UR	RW	RW	1	Protection context 2, user read enable.
17	PC2_UW	RW	RW	1	Protection context 2, user write enable.
18	PC2_PR	RW	RW	1	Protection context 2, privileged read enable.
19	PC2_PW	RW	RW	1	Protection context 2, privileged write enable.
20	PC2_NS	RW	RW	1	Protection context 2, non-secure.
24	PC3_UR	RW	RW	1	Protection context 3, user read enable.
25	PC3_UW	RW	RW	1	Protection context 3, user write enable.
26	PC3_PR	RW	RW	1	Protection context 3, privileged read enable.
27	PC3_PW	RW	RW	1	Protection context 3, privileged write enable.
28	PC3_NS	RW	RW	1	Protection context 3, non-secure.

21.596.1.4 PERI_MS_PPU_PR_SL_ATT1

Description: Slave attributes 1
Address: 0x40020014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC4_NS [4:4]	PC4_PW [3:3]	PC4_PR [2:2]	PC4_UW [1:1]	PC4_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC5_NS [12:12]	PC5_PW [11:11]	PC5_PR [10:10]	PC5_UW [9:9]	PC5_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC6_NS [20:20]	PC6_PW [19:19]	PC6_PR [18:18]	PC6_UW [17:17]	PC6_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC7_NS [28:28]	PC7_PW [27:27]	PC7_PR [26:26]	PC7_UW [25:25]	PC7_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC4_UR	RW	RW	1	Protection context 4, user read enable.
1	PC4_UW	RW	RW	1	Protection context 4, user write enable.
2	PC4_PR	RW	RW	1	Protection context 4, privileged read enable.
3	PC4_PW	RW	RW	1	Protection context 4, privileged write enable.
4	PC4_NS	RW	RW	1	Protection context 4, non-secure.
8	PC5_UR	RW	RW	1	Protection context 5, user read enable.
9	PC5_UW	RW	RW	1	Protection context 5, user write enable.
10	PC5_PR	RW	RW	1	Protection context 5, privileged read enable.
11	PC5_PW	RW	RW	1	Protection context 5, privileged write enable.
12	PC5_NS	RW	RW	1	Protection context 5, non-secure.
16	PC6_UR	RW	RW	1	Protection context 6, user read enable.
17	PC6_UW	RW	RW	1	Protection context 6, user write enable.
18	PC6_PR	RW	RW	1	Protection context 6, privileged read enable.
19	PC6_PW	RW	RW	1	Protection context 6, privileged write enable.
20	PC6_NS	RW	RW	1	Protection context 6, non-secure.
24	PC7_UR	RW	RW	1	Protection context 7, user read enable.
25	PC7_UW	RW	RW	1	Protection context 7, user write enable.
26	PC7_PR	RW	RW	1	Protection context 7, privileged read enable.
27	PC7_PW	RW	RW	1	Protection context 7, privileged write enable.
28	PC7_NS	RW	RW	1	Protection context 7, non-secure.

21.596.1.5 PERI_MS_PPU_PR_SL_ATT2

Description: Slave attributes 2
Address: 0x40020018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC8_NS [4:4]	PC8_PW [3:3]	PC8_PR [2:2]	PC8_UW [1:1]	PC8_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC9_NS [12:12]	PC9_PW [11:11]	PC9_PR [10:10]	PC9_UW [9:9]	PC9_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC10_NS [20:20]	PC10_PW [19:19]	PC10_PR [18:18]	PC10_UW [17:17]	PC10_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC11_NS [28:28]	PC11_PW [27:27]	PC11_PR [26:26]	PC11_UW [25:25]	PC11_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC8_UR	RW	RW	1	Protection context 8, user read enable.
1	PC8_UW	RW	RW	1	Protection context 8, user write enable.
2	PC8_PR	RW	RW	1	Protection context 8, privileged read enable.
3	PC8_PW	RW	RW	1	Protection context 8, privileged write enable.
4	PC8_NS	RW	RW	1	Protection context 8, non-secure.
8	PC9_UR	RW	RW	1	Protection context 9, user read enable.
9	PC9_UW	RW	RW	1	Protection context 9, user write enable.
10	PC9_PR	RW	RW	1	Protection context 9, privileged read enable.
11	PC9_PW	RW	RW	1	Protection context 9, privileged write enable.
12	PC9_NS	RW	RW	1	Protection context 9, non-secure.
16	PC10_UR	RW	RW	1	Protection context 10, user read enable.
17	PC10_UW	RW	RW	1	Protection context 10, user write enable.
18	PC10_PR	RW	RW	1	Protection context 10, privileged read enable.
19	PC10_PW	RW	RW	1	Protection context 10, privileged write enable.
20	PC10_NS	RW	RW	1	Protection context 10, non-secure.
24	PC11_UR	RW	RW	1	Protection context 11, user read enable.
25	PC11_UW	RW	RW	1	Protection context 11, user write enable.
26	PC11_PR	RW	RW	1	Protection context 11, privileged read enable.
27	PC11_PW	RW	RW	1	Protection context 11, privileged write enable.
28	PC11_NS	RW	RW	1	Protection context 11, non-secure.

21.596.1.6 PERI_MS_PPU_PR_SL_ATT3

Description: Slave attributes 3
Address: 0x4002001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC12_NS [4:4]	PC12_PW [3:3]	PC12_PR [2:2]	PC12_UW [1:1]	PC12_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC13_NS [12:12]	PC13_PW [11:11]	PC13_PR [10:10]	PC13_UW [9:9]	PC13_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC14_NS [20:20]	PC14_PW [19:19]	PC14_PR [18:18]	PC14_UW [17:17]	PC14_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC15_NS [28:28]	PC15_PW [27:27]	PC15_PR [26:26]	PC15_UW [25:25]	PC15_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC12_UR	RW	RW	1	Protection context 12, user read enable.
1	PC12_UW	RW	RW	1	Protection context 12, user write enable.
2	PC12_PR	RW	RW	1	Protection context 12, privileged read enable.
3	PC12_PW	RW	RW	1	Protection context 12, privileged write enable.
4	PC12_NS	RW	RW	1	Protection context 12, non-secure.
8	PC13_UR	RW	RW	1	Protection context 13, user read enable.
9	PC13_UW	RW	RW	1	Protection context 13, user write enable.
10	PC13_PR	RW	RW	1	Protection context 13, privileged read enable.
11	PC13_PW	RW	RW	1	Protection context 13, privileged write enable.
12	PC13_NS	RW	RW	1	Protection context 13, non-secure.
16	PC14_UR	RW	RW	1	Protection context 14, user read enable.
17	PC14_UW	RW	RW	1	Protection context 14, user write enable.
18	PC14_PR	RW	RW	1	Protection context 14, privileged read enable.
19	PC14_PW	RW	RW	1	Protection context 14, privileged write enable.
20	PC14_NS	RW	RW	1	Protection context 14, non-secure.
24	PC15_UR	RW	RW	1	Protection context 15, user read enable.
25	PC15_UW	RW	RW	1	Protection context 15, user write enable.
26	PC15_PR	RW	RW	1	Protection context 15, privileged read enable.
27	PC15_PW	RW	RW	1	Protection context 15, privileged write enable.
28	PC15_NS	RW	RW	1	Protection context 15, non-secure.

21.596.1.7 PERI_MS_PPU_PR_MS_ADDR

Description: Master region, base address
Address: 0x40020020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: MS_ADDR is fixed (non-programmable).

Default: The access privileges for MS_ADDR are determined by MS_ATT0, ..., MS_ATT3.
 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name								None [5:0]

Bits	15	14	13	12	11	10	9	8
Name								ADDR26 [15:8]

Bits	23	22	21	20	19	18	17	16
Name								ADDR26 [23:16]

Bits	31	30	29	28	27	26	25	24
Name								ADDR26 [31:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
6:31	ADDR26	R	R	ADDR1_DEF	This field specifies the base address of the master region. The base address of the region is the address of the SL_ADDR register.

21.596.1.8 PERI_MS_PPU_PR_MS_SIZE

Description: Master region, size
Address: 0x40020024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: MS_SIZE is fixed (non-programmable).

Default: The access privileges for MS_SIZE are determined by MS_ATT0, ..., MS_ATT3.
 0x85000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:29]		REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
24:28	REGION_SIZE	R	R	5	This field specifies the size of the master region: '5': 64 B region The master region includes the SL_ADDR, SL_SIZE, SL_ATT0, ..., SL_ATT3, MS_ADDR, MS_SIZE, MS_ATT0, ..., MS_ATT3 registers. Therefore, the access privileges for all these registers is determined by MS_ATT0, ..., MS_ATT3.
31	VALID	R	R	1	Master region enable: '1': Enabled.

21.596.1.9 PERI_MS_PPU_PR_MS_ATT0

Description: Master attributes 0
Address: 0x40020030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment: The access privileges for MS_ATT0, ..., MS_ATT3 are determined by MS_ATT0, ..., MS_ATT3.

Note that protection context '0' has unrestricted access: PC0_UR, ..., PC0_NS fields are fixed to '1's. The other protection contexts have SW programmable fields.

Typically, the MS_ATT0, ..., MS_ATT3 registers are programmed by the boot process with protection context '0'.

Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC0_NS [4:4]	PC0_PW [3:3]	PC0_PR [2:2]	PC0_UW [1:1]	PC0_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC1_NS [12:12]	PC1_PW [11:11]	PC1_PR [10:10]	PC1_UW [9:9]	PC1_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC2_NS [20:20]	PC2_PW [19:19]	PC2_PR [18:18]	PC2_UW [17:17]	PC2_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC3_NS [28:28]	PC3_PW [27:27]	PC3_PR [26:26]	PC3_UW [25:25]	PC3_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC0_UR	R	R	1	Protection context 0, user read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	PC0_UW	R	R	1	Protection context 0, user write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	PC0_PR	R	R	1	Protection context 0, privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
3	PC0_PW	R	R	1	Protection context 0, privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).
4	PC0_NS	R	R	1	Protection context 0, non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC1_UR	R	R	1	Protection context 1, user read enable.
9	PC1_UW	RW	RW	1	Protection context 1, user write enable.
10	PC1_PR	R	R	1	Protection context 1, privileged read enable.
11	PC1_PW	RW	RW	1	Protection context 1, privileged write enable.

Bits	Name	SW	HW	Default or Enum	Description
12	PC1_NS	RW	RW	1	Protection context 1, non-secure.
16	PC2_UR	R	R	1	Protection context 2, user read enable.
17	PC2_UW	RW	RW	1	Protection context 2, user write enable.
18	PC2_PR	R	R	1	Protection context 2, privileged read enable.
19	PC2_PW	RW	RW	1	Protection context 2, privileged write enable.
20	PC2_NS	RW	RW	1	Protection context 2, non-secure.
24	PC3_UR	R	R	1	Protection context 3, user read enable.
25	PC3_UW	RW	RW	1	Protection context 3, user write enable.
26	PC3_PR	R	R	1	Protection context 3, privileged read enable.
27	PC3_PW	RW	RW	1	Protection context 3, privileged write enable.
28	PC3_NS	RW	RW	1	Protection context 3, non-secure.

21.596.1.10 PERI_MS_PPU_PR_MS_ATT1

Description: Master attributes 1
Address: 0x40020034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC4_NS [4:4]	PC4_PW [3:3]	PC4_PR [2:2]	PC4_UW [1:1]	PC4_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC5_NS [12:12]	PC5_PW [11:11]	PC5_PR [10:10]	PC5_UW [9:9]	PC5_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC6_NS [20:20]	PC6_PW [19:19]	PC6_PR [18:18]	PC6_UW [17:17]	PC6_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC7_NS [28:28]	PC7_PW [27:27]	PC7_PR [26:26]	PC7_UW [25:25]	PC7_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC4_UR	R	R	1	Protection context 4, user read enable.
1	PC4_UW	RW	RW	1	Protection context 4, user write enable.
2	PC4_PR	R	R	1	Protection context 4, privileged read enable.
3	PC4_PW	RW	RW	1	Protection context 4, privileged write enable.
4	PC4_NS	RW	RW	1	Protection context 4, non-secure.
8	PC5_UR	R	R	1	Protection context 5, user read enable.
9	PC5_UW	RW	RW	1	Protection context 5, user write enable.
10	PC5_PR	R	R	1	Protection context 5, privileged read enable.
11	PC5_PW	RW	RW	1	Protection context 5, privileged write enable.
12	PC5_NS	RW	RW	1	Protection context 5, non-secure.
16	PC6_UR	R	R	1	Protection context 6, user read enable.
17	PC6_UW	RW	RW	1	Protection context 6, user write enable.
18	PC6_PR	R	R	1	Protection context 6, privileged read enable.
19	PC6_PW	RW	RW	1	Protection context 6, privileged write enable.
20	PC6_NS	RW	RW	1	Protection context 6, non-secure.
24	PC7_UR	R	R	1	Protection context 7, user read enable.
25	PC7_UW	RW	RW	1	Protection context 7, user write enable.
26	PC7_PR	R	R	1	Protection context 7, privileged read enable.
27	PC7_PW	RW	RW	1	Protection context 7, privileged write enable.
28	PC7_NS	RW	RW	1	Protection context 7, non-secure.

21.596.1.11 PERI_MS_PPU_PR_MS_ATT2

Description: Master attributes 2
Address: 0x40020038
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC8_NS [4:4]	PC8_PW [3:3]	PC8_PR [2:2]	PC8_UW [1:1]	PC8_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC9_NS [12:12]	PC9_PW [11:11]	PC9_PR [10:10]	PC9_UW [9:9]	PC9_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC10_NS [20:20]	PC10_PW [19:19]	PC10_PR [18:18]	PC10_UW [17:17]	PC10_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC11_NS [28:28]	PC11_PW [27:27]	PC11_PR [26:26]	PC11_UW [25:25]	PC11_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC8_UR	R	R	1	Protection context 8, user read enable.
1	PC8_UW	RW	RW	1	Protection context 8, user write enable.
2	PC8_PR	R	R	1	Protection context 8, privileged read enable.
3	PC8_PW	RW	RW	1	Protection context 8, privileged write enable.
4	PC8_NS	RW	RW	1	Protection context 8, non-secure.
8	PC9_UR	R	R	1	Protection context 9, user read enable.
9	PC9_UW	RW	RW	1	Protection context 9, user write enable.
10	PC9_PR	R	R	1	Protection context 9, privileged read enable.
11	PC9_PW	RW	RW	1	Protection context 9, privileged write enable.
12	PC9_NS	RW	RW	1	Protection context 9, non-secure.
16	PC10_UR	R	R	1	Protection context 10, user read enable.
17	PC10_UW	RW	RW	1	Protection context 10, user write enable.
18	PC10_PR	R	R	1	Protection context 10, privileged read enable.
19	PC10_PW	RW	RW	1	Protection context 10, privileged write enable.
20	PC10_NS	RW	RW	1	Protection context 10, non-secure.
24	PC11_UR	R	R	1	Protection context 11, user read enable.
25	PC11_UW	RW	RW	1	Protection context 11, user write enable.
26	PC11_PR	R	R	1	Protection context 11, privileged read enable.
27	PC11_PW	RW	RW	1	Protection context 11, privileged write enable.
28	PC11_NS	RW	RW	1	Protection context 11, non-secure.

21.596.1.12 PERI_MS_PPU_PR_MS_ATT3

Description: Master attributes 3
Address: 0x4002003C
Offset: 0x3C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC12_NS [4:4]	PC12_PW [3:3]	PC12_PR [2:2]	PC12_UW [1:1]	PC12_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC13_NS [12:12]	PC13_PW [11:11]	PC13_PR [10:10]	PC13_UW [9:9]	PC13_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC14_NS [20:20]	PC14_PW [19:19]	PC14_PR [18:18]	PC14_UW [17:17]	PC14_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC15_NS [28:28]	PC15_PW [27:27]	PC15_PR [26:26]	PC15_UW [25:25]	PC15_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC12_UR	R	R	1	Protection context 12, user read enable.
1	PC12_UW	RW	RW	1	Protection context 12, user write enable.
2	PC12_PR	R	R	1	Protection context 12, privileged read enable.
3	PC12_PW	RW	RW	1	Protection context 12, privileged write enable.
4	PC12_NS	RW	RW	1	Protection context 12, non-secure.
8	PC13_UR	R	R	1	Protection context 13, user read enable.
9	PC13_UW	RW	RW	1	Protection context 13, user write enable.
10	PC13_PR	R	R	1	Protection context 13, privileged read enable.
11	PC13_PW	RW	RW	1	Protection context 13, privileged write enable.
12	PC13_NS	RW	RW	1	Protection context 13, non-secure.
16	PC14_UR	R	R	1	Protection context 14, user read enable.
17	PC14_UW	RW	RW	1	Protection context 14, user write enable.
18	PC14_PR	R	R	1	Protection context 14, privileged read enable.
19	PC14_PW	RW	RW	1	Protection context 14, privileged write enable.
20	PC14_NS	RW	RW	1	Protection context 14, non-secure.
24	PC15_UR	R	R	1	Protection context 15, user read enable.
25	PC15_UW	RW	RW	1	Protection context 15, user write enable.
26	PC15_PR	R	R	1	Protection context 15, privileged read enable.
27	PC15_PW	RW	RW	1	Protection context 15, privileged write enable.
28	PC15_NS	RW	RW	1	Protection context 15, non-secure.

21.596.2 PPU_FX

21.596.2.1 PERI_MS_PPU_FX_SL_ADDR

Description: Slave region, base address
Address: 0x40020800
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: SL_ADDR is fixed (non-programmable).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name							None [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	ADDR30 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR30 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR30 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
2:31	ADDR30	R	R	ADDR0_DEF	This field specifies the base address of the slave region. The region size is defined by SL_SIZE.REGION_SIZE. A region of n Bytes must be n Byte aligned. Therefore, some of the lesser significant address bits of ADDR30 must be '0's. E.g., a 64 KB address region (REGION_SIZE is '15') must be 64 KByte aligned, and ADDR30[13:0] must be '0's.

21.596.2.2 PERI_MS_PPU_FX_SL_SIZE

Description: Slave region, size
Address: 0x40020804
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: SL_SIZE is fixed (non-programmable).
Default: 0x80000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:29]		REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
24:28	REGION_SIZE	R	R	REGION_SIZE0_DEF	This field specifies the size of the slave region: '0': Undefined. '1': 4 B region (this is the smallest region size). '2': 8 B region '3': 16 B region '4': 32 B region '5': 64 B region '6': 128 B region '7': 256 B region '8': 512 B region '9': 1 KB region '10': 2 KB region '11': 4 KB region '12': 8 KB region '13': 16 KB region '14': 32 KB region '15': 64 KB region '16': 128 KB region '17': 256 KB region '18': 512 KB region '19': 1 MB region '20': 2 MB region '21': 4 MB region '22': 8 MB region '23': 16 MB region '24': 32 MB region '25': 64 MB region '26': 128 MB region '27': 256 MB region '28': 512 MB region '29': 1 GB region '30': 2 GB region '31': 4 GB region

Bits	Name	SW	HW	Default or Enum	Description
31	VALID	R	R	1	Slave region enable: '0': Disabled. A disabled region will never result in a match on the transfer address. '1': Enabled.

21.596.2.3 PERI_MS_PPU_FX_SL_ATT0

Description: Slave attributes 0
Address: 0x40020810
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: The access privileges for SL_ATT0, ..., SL_ATT3 are determined by MS_ATT0, ..., MS_ATT3.

Note that protection context '0' has unrestricted access: PC0_UR, ..., PC0_NS fields are fixed to '1's. The other protection contexts have SW programmable fields.

Typically, the SL_ATT0, ..., SL_ATT3 registers are initialized by the boot process with protection context '0'.

For 4 or less protection contexts (PC_NR ≤ 4), only SL_ATT0 is present. For 5 through 8 protection contexts, only SL_ATT0 and SL_ATT1 are present. For 9 through 12 or less protection contexts, only SL_ATT0, SL_ATT1 and SL_ATT2 are present. For 13 through 16 protection contexts, SL_ATT0, SL_ATT1, SL_ATT2 and SL_ATT3 are all present. If the number of protection contexts is not a multiple of 4, the 'missing' protection contexts in a register have no associated access fields (and the field positions read as '0').

Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC0_NS [4:4]	PC0_PW [3:3]	PC0_PR [2:2]	PC0_UW [1:1]	PC0_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC1_NS [12:12]	PC1_PW [11:11]	PC1_PR [10:10]	PC1_UW [9:9]	PC1_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC2_NS [20:20]	PC2_PW [19:19]	PC2_PR [18:18]	PC2_UW [17:17]	PC2_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC3_NS [28:28]	PC3_PW [27:27]	PC3_PR [26:26]	PC3_UW [25:25]	PC3_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC0_UR	R	R	1	Protection context 0, user read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	PC0_UW	R	R	1	Protection context 0, user write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	PC0_PR	R	R	1	Protection context 0, privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
3	PC0_PW	R	R	1	Protection context 0, privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).

Bits	Name	SW	HW	Default or Enum	Description
4	PC0_NS	R	R	1	Protection context 0, non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC1_UR	RW	RW	1	Protection context 1, user read enable.
9	PC1_UW	RW	RW	1	Protection context 1, user write enable.
10	PC1_PR	RW	RW	1	Protection context 1, privileged read enable.
11	PC1_PW	RW	RW	1	Protection context 1, privileged write enable.
12	PC1_NS	RW	RW	1	Protection context 1, non-secure.
16	PC2_UR	RW	RW	1	Protection context 2, user read enable.
17	PC2_UW	RW	RW	1	Protection context 2, user write enable.
18	PC2_PR	RW	RW	1	Protection context 2, privileged read enable.
19	PC2_PW	RW	RW	1	Protection context 2, privileged write enable.
20	PC2_NS	RW	RW	1	Protection context 2, non-secure.
24	PC3_UR	RW	RW	1	Protection context 3, user read enable.
25	PC3_UW	RW	RW	1	Protection context 3, user write enable.
26	PC3_PR	RW	RW	1	Protection context 3, privileged read enable.
27	PC3_PW	RW	RW	1	Protection context 3, privileged write enable.
28	PC3_NS	RW	RW	1	Protection context 3, non-secure.

21.596.2.4 PERI_MS_PPU_FX_SL_ATT1

Description: Slave attributes 1
Address: 0x40020814
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC4_NS [4:4]	PC4_PW [3:3]	PC4_PR [2:2]	PC4_UW [1:1]	PC4_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC5_NS [12:12]	PC5_PW [11:11]	PC5_PR [10:10]	PC5_UW [9:9]	PC5_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC6_NS [20:20]	PC6_PW [19:19]	PC6_PR [18:18]	PC6_UW [17:17]	PC6_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC7_NS [28:28]	PC7_PW [27:27]	PC7_PR [26:26]	PC7_UW [25:25]	PC7_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC4_UR	RW	RW	1	Protection context 4, user read enable.
1	PC4_UW	RW	RW	1	Protection context 4, user write enable.
2	PC4_PR	RW	RW	1	Protection context 4, privileged read enable.
3	PC4_PW	RW	RW	1	Protection context 4, privileged write enable.
4	PC4_NS	RW	RW	1	Protection context 4, non-secure.
8	PC5_UR	RW	RW	1	Protection context 5, user read enable.
9	PC5_UW	RW	RW	1	Protection context 5, user write enable.
10	PC5_PR	RW	RW	1	Protection context 5, privileged read enable.
11	PC5_PW	RW	RW	1	Protection context 5, privileged write enable.
12	PC5_NS	RW	RW	1	Protection context 5, non-secure.
16	PC6_UR	RW	RW	1	Protection context 6, user read enable.
17	PC6_UW	RW	RW	1	Protection context 6, user write enable.
18	PC6_PR	RW	RW	1	Protection context 6, privileged read enable.
19	PC6_PW	RW	RW	1	Protection context 6, privileged write enable.
20	PC6_NS	RW	RW	1	Protection context 6, non-secure.
24	PC7_UR	RW	RW	1	Protection context 7, user read enable.
25	PC7_UW	RW	RW	1	Protection context 7, user write enable.
26	PC7_PR	RW	RW	1	Protection context 7, privileged read enable.
27	PC7_PW	RW	RW	1	Protection context 7, privileged write enable.
28	PC7_NS	RW	RW	1	Protection context 7, non-secure.

21.596.2.5 PERI_MS_PPU_FX_SL_ATT2

Description: Slave attributes 2
Address: 0x40020818
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC8_NS [4:4]	PC8_PW [3:3]	PC8_PR [2:2]	PC8_UW [1:1]	PC8_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC9_NS [12:12]	PC9_PW [11:11]	PC9_PR [10:10]	PC9_UW [9:9]	PC9_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC10_NS [20:20]	PC10_PW [19:19]	PC10_PR [18:18]	PC10_UW [17:17]	PC10_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC11_NS [28:28]	PC11_PW [27:27]	PC11_PR [26:26]	PC11_UW [25:25]	PC11_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC8_UR	RW	RW	1	Protection context 8, user read enable.
1	PC8_UW	RW	RW	1	Protection context 8, user write enable.
2	PC8_PR	RW	RW	1	Protection context 8, privileged read enable.
3	PC8_PW	RW	RW	1	Protection context 8, privileged write enable.
4	PC8_NS	RW	RW	1	Protection context 8, non-secure.
8	PC9_UR	RW	RW	1	Protection context 9, user read enable.
9	PC9_UW	RW	RW	1	Protection context 9, user write enable.
10	PC9_PR	RW	RW	1	Protection context 9, privileged read enable.
11	PC9_PW	RW	RW	1	Protection context 9, privileged write enable.
12	PC9_NS	RW	RW	1	Protection context 9, non-secure.
16	PC10_UR	RW	RW	1	Protection context 10, user read enable.
17	PC10_UW	RW	RW	1	Protection context 10, user write enable.
18	PC10_PR	RW	RW	1	Protection context 10, privileged read enable.
19	PC10_PW	RW	RW	1	Protection context 10, privileged write enable.
20	PC10_NS	RW	RW	1	Protection context 10, non-secure.
24	PC11_UR	RW	RW	1	Protection context 11, user read enable.
25	PC11_UW	RW	RW	1	Protection context 11, user write enable.
26	PC11_PR	RW	RW	1	Protection context 11, privileged read enable.
27	PC11_PW	RW	RW	1	Protection context 11, privileged write enable.
28	PC11_NS	RW	RW	1	Protection context 11, non-secure.

21.596.2.6 PERI_MS_PPU_FX_SL_ATT3

Description: Slave attributes 3
Address: 0x4002081C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC12_NS [4:4]	PC12_PW [3:3]	PC12_PR [2:2]	PC12_UW [1:1]	PC12_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC13_NS [12:12]	PC13_PW [11:11]	PC13_PR [10:10]	PC13_UW [9:9]	PC13_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC14_NS [20:20]	PC14_PW [19:19]	PC14_PR [18:18]	PC14_UW [17:17]	PC14_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC15_NS [28:28]	PC15_PW [27:27]	PC15_PR [26:26]	PC15_UW [25:25]	PC15_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC12_UR	RW	RW	1	Protection context 12, user read enable.
1	PC12_UW	RW	RW	1	Protection context 12, user write enable.
2	PC12_PR	RW	RW	1	Protection context 12, privileged read enable.
3	PC12_PW	RW	RW	1	Protection context 12, privileged write enable.
4	PC12_NS	RW	RW	1	Protection context 12, non-secure.
8	PC13_UR	RW	RW	1	Protection context 13, user read enable.
9	PC13_UW	RW	RW	1	Protection context 13, user write enable.
10	PC13_PR	RW	RW	1	Protection context 13, privileged read enable.
11	PC13_PW	RW	RW	1	Protection context 13, privileged write enable.
12	PC13_NS	RW	RW	1	Protection context 13, non-secure.
16	PC14_UR	RW	RW	1	Protection context 14, user read enable.
17	PC14_UW	RW	RW	1	Protection context 14, user write enable.
18	PC14_PR	RW	RW	1	Protection context 14, privileged read enable.
19	PC14_PW	RW	RW	1	Protection context 14, privileged write enable.
20	PC14_NS	RW	RW	1	Protection context 14, non-secure.
24	PC15_UR	RW	RW	1	Protection context 15, user read enable.
25	PC15_UW	RW	RW	1	Protection context 15, user write enable.
26	PC15_PR	RW	RW	1	Protection context 15, privileged read enable.
27	PC15_PW	RW	RW	1	Protection context 15, privileged write enable.
28	PC15_NS	RW	RW	1	Protection context 15, non-secure.

21.596.2.7 PERI_MS_PPU_FX_MS_ADDR

Description: Master region, base address
Address: 0x40020820
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: MS_ADDR is fixed (non-programmable).

Default: The access privileges for MS_ADDR are determined by MS_ATT0, ..., MS_ATT3.
 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name								None [5:0]

Bits	15	14	13	12	11	10	9	8
Name								ADDR26 [15:8]

Bits	23	22	21	20	19	18	17	16
Name								ADDR26 [23:16]

Bits	31	30	29	28	27	26	25	24
Name								ADDR26 [31:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
6:31	ADDR26	R	R	ADDR1_DEF	This field specifies the base address of the master region. The base address of the region is the address of the SL_ADDR register.

21.596.2.8 PERI_MS_PPU_FX_MS_SIZE

Description: Master region, size
Address: 0x40020824
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: MS_SIZE is fixed (non-programmable).

Default: The access privileges for MS_SIZE are determined by MS_ATT0, ..., MS_ATT3.
 0x85000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	VALID [31:31]	None [30:29]		REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
24:28	REGION_SIZE	R	R	5	This field specifies the size of the master region: '5': 64 B region The master region includes the SL_ADDR, SL_SIZE, SL_ATT0, ..., SL_ATT3, MS_ADDR, MS_SIZE, MS_ATT0, ..., MS_ATT3 registers. Therefore, the access privileges for all these registers is determined by MS_ATT0, ..., MS_ATT3.
31	VALID	R	R	1	Master region enable: '1': Enabled.

21.596.2.9 PERI_MS_PPU_FX_MS_ATT0

Description: Master attributes 0
Address: 0x40020830
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment: The access privileges for MS_ATT0, ..., MS_ATT3 are determined by MS_ATT0, ..., MS_ATT3.

Note that protection context '0' has unrestricted access: PC0_UR, ..., PC0_NS fields are fixed to '1's. The other protection contexts have SW programmable fields.

Typically, the MS_ATT0, ..., MS_ATT3 registers are programmed by the boot process with protection context '0'.

Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC0_NS [4:4]	PC0_PW [3:3]	PC0_PR [2:2]	PC0_UW [1:1]	PC0_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC1_NS [12:12]	PC1_PW [11:11]	PC1_PR [10:10]	PC1_UW [9:9]	PC1_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC2_NS [20:20]	PC2_PW [19:19]	PC2_PR [18:18]	PC2_UW [17:17]	PC2_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC3_NS [28:28]	PC3_PW [27:27]	PC3_PR [26:26]	PC3_UW [25:25]	PC3_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC0_UR	R	R	1	Protection context 0, user read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	PC0_UW	R	R	1	Protection context 0, user write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	PC0_PR	R	R	1	Protection context 0, privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
3	PC0_PW	R	R	1	Protection context 0, privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).
4	PC0_NS	R	R	1	Protection context 0, non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC1_UR	R	R	1	Protection context 1, user read enable.
9	PC1_UW	RW	RW	1	Protection context 1, user write enable.
10	PC1_PR	R	R	1	Protection context 1, privileged read enable.
11	PC1_PW	RW	RW	1	Protection context 1, privileged write enable.

Bits	Name	SW	HW	Default or Enum	Description
12	PC1_NS	RW	RW	1	Protection context 1, non-secure.
16	PC2_UR	R	R	1	Protection context 2, user read enable.
17	PC2_UW	RW	RW	1	Protection context 2, user write enable.
18	PC2_PR	R	R	1	Protection context 2, privileged read enable.
19	PC2_PW	RW	RW	1	Protection context 2, privileged write enable.
20	PC2_NS	RW	RW	1	Protection context 2, non-secure.
24	PC3_UR	R	R	1	Protection context 3, user read enable.
25	PC3_UW	RW	RW	1	Protection context 3, user write enable.
26	PC3_PR	R	R	1	Protection context 3, privileged read enable.
27	PC3_PW	RW	RW	1	Protection context 3, privileged write enable.
28	PC3_NS	RW	RW	1	Protection context 3, non-secure.

21.596.2.10 PERI_MS_PPU_FX_MS_ATT1

Description: Master attributes 1
Address: 0x40020834
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC4_NS [4:4]	PC4_PW [3:3]	PC4_PR [2:2]	PC4_UW [1:1]	PC4_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC5_NS [12:12]	PC5_PW [11:11]	PC5_PR [10:10]	PC5_UW [9:9]	PC5_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC6_NS [20:20]	PC6_PW [19:19]	PC6_PR [18:18]	PC6_UW [17:17]	PC6_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC7_NS [28:28]	PC7_PW [27:27]	PC7_PR [26:26]	PC7_UW [25:25]	PC7_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC4_UR	R	R	1	Protection context 4, user read enable.
1	PC4_UW	RW	RW	1	Protection context 4, user write enable.
2	PC4_PR	R	R	1	Protection context 4, privileged read enable.
3	PC4_PW	RW	RW	1	Protection context 4, privileged write enable.
4	PC4_NS	RW	RW	1	Protection context 4, non-secure.
8	PC5_UR	R	R	1	Protection context 5, user read enable.
9	PC5_UW	RW	RW	1	Protection context 5, user write enable.
10	PC5_PR	R	R	1	Protection context 5, privileged read enable.
11	PC5_PW	RW	RW	1	Protection context 5, privileged write enable.
12	PC5_NS	RW	RW	1	Protection context 5, non-secure.
16	PC6_UR	R	R	1	Protection context 6, user read enable.
17	PC6_UW	RW	RW	1	Protection context 6, user write enable.
18	PC6_PR	R	R	1	Protection context 6, privileged read enable.
19	PC6_PW	RW	RW	1	Protection context 6, privileged write enable.
20	PC6_NS	RW	RW	1	Protection context 6, non-secure.
24	PC7_UR	R	R	1	Protection context 7, user read enable.
25	PC7_UW	RW	RW	1	Protection context 7, user write enable.
26	PC7_PR	R	R	1	Protection context 7, privileged read enable.
27	PC7_PW	RW	RW	1	Protection context 7, privileged write enable.
28	PC7_NS	RW	RW	1	Protection context 7, non-secure.

21.596.2.11 PERI_MS_PPU_FX_MS_ATT2

Description: Master attributes 2
Address: 0x40020838
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC8_NS [4:4]	PC8_PW [3:3]	PC8_PR [2:2]	PC8_UW [1:1]	PC8_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC9_NS [12:12]	PC9_PW [11:11]	PC9_PR [10:10]	PC9_UW [9:9]	PC9_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC10_NS [20:20]	PC10_PW [19:19]	PC10_PR [18:18]	PC10_UW [17:17]	PC10_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC11_NS [28:28]	PC11_PW [27:27]	PC11_PR [26:26]	PC11_UW [25:25]	PC11_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC8_UR	R	R	1	Protection context 8, user read enable.
1	PC8_UW	RW	RW	1	Protection context 8, user write enable.
2	PC8_PR	R	R	1	Protection context 8, privileged read enable.
3	PC8_PW	RW	RW	1	Protection context 8, privileged write enable.
4	PC8_NS	RW	RW	1	Protection context 8, non-secure.
8	PC9_UR	R	R	1	Protection context 9, user read enable.
9	PC9_UW	RW	RW	1	Protection context 9, user write enable.
10	PC9_PR	R	R	1	Protection context 9, privileged read enable.
11	PC9_PW	RW	RW	1	Protection context 9, privileged write enable.
12	PC9_NS	RW	RW	1	Protection context 9, non-secure.
16	PC10_UR	R	R	1	Protection context 10, user read enable.
17	PC10_UW	RW	RW	1	Protection context 10, user write enable.
18	PC10_PR	R	R	1	Protection context 10, privileged read enable.
19	PC10_PW	RW	RW	1	Protection context 10, privileged write enable.
20	PC10_NS	RW	RW	1	Protection context 10, non-secure.
24	PC11_UR	R	R	1	Protection context 11, user read enable.
25	PC11_UW	RW	RW	1	Protection context 11, user write enable.
26	PC11_PR	R	R	1	Protection context 11, privileged read enable.
27	PC11_PW	RW	RW	1	Protection context 11, privileged write enable.
28	PC11_NS	RW	RW	1	Protection context 11, non-secure.

21.596.2.12 PERI_MS_PPU_FX_MS_ATT3

Description: Master attributes 3
Address: 0x4002083C
Offset: 0x3C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1F1F1F1F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PC12_NS [4:4]	PC12_PW [3:3]	PC12_PR [2:2]	PC12_UW [1:1]	PC12_UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			PC13_NS [12:12]	PC13_PW [11:11]	PC13_PR [10:10]	PC13_UW [9:9]	PC13_UR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			PC14_NS [20:20]	PC14_PW [19:19]	PC14_PR [18:18]	PC14_UW [17:17]	PC14_UR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			PC15_NS [28:28]	PC15_PW [27:27]	PC15_PR [26:26]	PC15_UW [25:25]	PC15_UR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	PC12_UR	R	R	1	Protection context 12, user read enable.
1	PC12_UW	RW	RW	1	Protection context 12, user write enable.
2	PC12_PR	R	R	1	Protection context 12, privileged read enable.
3	PC12_PW	RW	RW	1	Protection context 12, privileged write enable.
4	PC12_NS	RW	RW	1	Protection context 12, non-secure.
8	PC13_UR	R	R	1	Protection context 13, user read enable.
9	PC13_UW	RW	RW	1	Protection context 13, user write enable.
10	PC13_PR	R	R	1	Protection context 13, privileged read enable.
11	PC13_PW	RW	RW	1	Protection context 13, privileged write enable.
12	PC13_NS	RW	RW	1	Protection context 13, non-secure.
16	PC14_UR	R	R	1	Protection context 14, user read enable.
17	PC14_UW	RW	RW	1	Protection context 14, user write enable.
18	PC14_PR	R	R	1	Protection context 14, privileged read enable.
19	PC14_PW	RW	RW	1	Protection context 14, privileged write enable.
20	PC14_NS	RW	RW	1	Protection context 14, non-secure.
24	PC15_UR	R	R	1	Protection context 15, user read enable.
25	PC15_UW	RW	RW	1	Protection context 15, user write enable.
26	PC15_PR	R	R	1	Protection context 15, privileged read enable.
27	PC15_PW	RW	RW	1	Protection context 15, privileged write enable.
28	PC15_NS	RW	RW	1	Protection context 15, non-secure.

22 PERI_PCLK

Description	Peripheral PCLK groups
Base Address	0x40040000
Size	0x20000
Slave Num	MMIO0 - 2

22.1 GR 0

Register Name	Address	Permission	Description
PERI_PCLK_GR0_DIV_CMD	0x40040000	FULL	Divider command
PERI_PCLK_GR0_CLOCK_CTL0	0x40040C00	FULL	Clock control
PERI_PCLK_GR0_CLOCK_CTL1	0x40040C04	FULL	Clock control
PERI_PCLK_GR0_CLOCK_CTL2	0x40040C08	FULL	Clock control
PERI_PCLK_GR0_CLOCK_CTL3	0x40040C0C	FULL	Clock control
PERI_PCLK_GR0_CLOCK_CTL4	0x40040C10	FULL	Clock control
PERI_PCLK_GR0_CLOCK_CTL5	0x40040C14	FULL	Clock control
PERI_PCLK_GR0_DIV_8_CTL0	0x40041000	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR0_DIV_8_CTL1	0x40041004	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR0_DIV_8_CTL2	0x40041008	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR0_DIV_16_CTL0	0x40041400	FULL	Divider control (for 16.0 divider)

22.2 GR 1

Register Name	Address	Permission	Description
PERI_PCLK_GR1_DIV_CMD	0x40042000	FULL	Divider command
PERI_PCLK_GR1_CLOCK_CTL0	0x40042C00	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL1	0x40042C04	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL2	0x40042C08	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL3	0x40042C0C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL4	0x40042C10	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL5	0x40042C14	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL6	0x40042C18	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL7	0x40042C1C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL8	0x40042C20	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL9	0x40042C24	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL10	0x40042C28	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL11	0x40042C2C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL12	0x40042C30	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL13	0x40042C34	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL14	0x40042C38	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL15	0x40042C3C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL16	0x40042C40	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL17	0x40042C44	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL18	0x40042C48	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL19	0x40042C4C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL20	0x40042C50	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL21	0x40042C54	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL22	0x40042C58	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL23	0x40042C5C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL24	0x40042C60	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL25	0x40042C64	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL26	0x40042C68	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL27	0x40042C6C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL28	0x40042C70	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL29	0x40042C74	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL30	0x40042C78	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL31	0x40042C7C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL32	0x40042C80	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL33	0x40042C84	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL34	0x40042C88	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL35	0x40042C8C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL36	0x40042C90	FULL	Clock control

Register Name	Address	Permission	Description
PERI_PCLK_GR1_CLOCK_CTL37	0x40042C94	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL38	0x40042C98	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL39	0x40042C9C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL40	0x40042CA0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL41	0x40042CA4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL42	0x40042CA8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL43	0x40042CAC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL44	0x40042CB0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL45	0x40042CB4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL46	0x40042CB8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL47	0x40042CBC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL48	0x40042CC0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL49	0x40042CC4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL50	0x40042CC8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL51	0x40042CCC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL52	0x40042CD0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL53	0x40042CD4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL54	0x40042CD8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL55	0x40042CDC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL56	0x40042CE0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL57	0x40042CE4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL58	0x40042CE8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL59	0x40042CEC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL60	0x40042CF0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL61	0x40042CF4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL62	0x40042CF8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL63	0x40042CFC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL64	0x40042D00	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL65	0x40042D04	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL66	0x40042D08	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL67	0x40042D0C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL68	0x40042D10	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL69	0x40042D14	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL70	0x40042D18	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL71	0x40042D1C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL72	0x40042D20	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL73	0x40042D24	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL74	0x40042D28	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL75	0x40042D2C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL76	0x40042D30	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL77	0x40042D34	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL78	0x40042D38	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL79	0x40042D3C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL80	0x40042D40	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL81	0x40042D44	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL82	0x40042D48	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL83	0x40042D4C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL84	0x40042D50	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL85	0x40042D54	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL86	0x40042D58	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL87	0x40042D5C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL88	0x40042D60	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL89	0x40042D64	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL90	0x40042D68	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL91	0x40042D6C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL92	0x40042D70	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL93	0x40042D74	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL94	0x40042D78	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL95	0x40042D7C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL96	0x40042D80	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL97	0x40042D84	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL98	0x40042D88	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL99	0x40042D8C	FULL	Clock control

Register Name	Address	Permission	Description
PERI_PCLK_GR1_CLOCK_CTL100	0x40042D90	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL101	0x40042D94	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL102	0x40042D98	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL103	0x40042D9C	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL104	0x40042DA0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL105	0x40042DA4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL106	0x40042DA8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL107	0x40042DAC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL108	0x40042DB0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL109	0x40042DB4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL110	0x40042DB8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL111	0x40042DBC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL112	0x40042DC0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL113	0x40042DC4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL114	0x40042DC8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL115	0x40042DCC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL116	0x40042DD0	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL117	0x40042DD4	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL118	0x40042DD8	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL119	0x40042DDC	FULL	Clock control
PERI_PCLK_GR1_CLOCK_CTL120	0x40042DE0	FULL	Clock control
PERI_PCLK_GR1_DIV_8_CTL0	0x40043000	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL1	0x40043004	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL2	0x40043008	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL3	0x4004300C	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL4	0x40043010	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL5	0x40043014	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL6	0x40043018	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL7	0x4004301C	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL8	0x40043020	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL9	0x40043024	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL10	0x40043028	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL11	0x4004302C	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL12	0x40043030	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL13	0x40043034	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL14	0x40043038	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_8_CTL15	0x4004303C	FULL	Divider control (for 8.0 divider)
PERI_PCLK_GR1_DIV_16_CTL0	0x40043400	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL1	0x40043404	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL2	0x40043408	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL3	0x4004340C	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL4	0x40043410	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL5	0x40043414	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL6	0x40043418	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL7	0x4004341C	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL8	0x40043420	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL9	0x40043424	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL10	0x40043428	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL11	0x4004342C	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL12	0x40043430	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL13	0x40043434	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL14	0x40043438	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL15	0x4004343C	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_16_CTL16	0x40043440	FULL	Divider control (for 16.0 divider)
PERI_PCLK_GR1_DIV_24_5_CTL0	0x40043C00	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL1	0x40043C04	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL2	0x40043C08	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL3	0x40043C0C	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL4	0x40043C10	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL5	0x40043C14	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL6	0x40043C18	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL7	0x40043C1C	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL8	0x40043C20	FULL	Divider control (for 24.5 divider)

Register Name	Address	Permission	Description
PERI_PCLK_GR1_DIV_24_5_CTL9	0x40043C24	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL10	0x40043C28	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL11	0x40043C2C	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL12	0x40043C30	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL13	0x40043C34	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL14	0x40043C38	FULL	Divider control (for 24.5 divider)
PERI_PCLK_GR1_DIV_24_5_CTL15	0x40043C3C	FULL	Divider control (for 24.5 divider)

22.3 Register Details

22.3.1 GR

22.3.1.1 PERI_PCLK_GR_DIV_CMD

Description: Divider command
Address: 0x40040000
Offset: 0x0
Retention: Not Retained
IsDeepSleep: No
Comment: The (PA_TYPE_SEL, PA_DIV_SEL) field pair allows a divider to be phase aligned with another divider. E.g., consider a 48 MHz 'clk_pclk_root[i]', and a need for a 12 MHz divided clock A and a 8 MHz divided clock B. Clock A uses 8.0 integer divider 0 and is created by aligning it to 'clk_pclk_root[i]' ((PA_TYPE_SEL, PA_DIV_SEL) is (3, 63)) and DIV_8_CTL0.INT8_DIV is '4-1'. Clock B uses 8.0 integer divider 1 and is created by aligning it to clock A ((PA_TYPE_SEL, PA_DIV_SEL) is (0, 0)) and DIV_8_CTL1.INT8_DIV is '6-1'. This guarantees that clock B is phase aligned with clock A: as the smallest common multiple of the two clock periods is 12 'clk_pclk_root[i]' cycles, the clocks A and B will be aligned every 12 'clk_pclk_root[i]' cycles. Note: clock B is phase aligned to clock A, but still uses 'clk_pclk_root[i]' as a reference clock for its divider value.
Default: 0x3FF03FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DIV_SEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						TYPE_SEL [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	PA_DIV_SEL [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	DISABLE [30:30]	None [29:26]				PA_TYPE_SEL [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DIV_SEL	RW	RW	255	(TYPE_SEL, DIV_SEL) specifies the divider on which the command (DISABLE/ENABLE) is performed. If DIV_SEL is '255' and TYPE_SEL is '3' (default/reset value), no divider is specified and no clock signal(s) are generated.
8:9	TYPE_SEL	RW	RW	3	Specifies the divider type of the divider on which the command is performed: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers.
16:23	PA_DIV_SEL	RW	RW	255	(PA_TYPE_SEL, PA_DIV_SEL) specifies the divider to which phase alignment is performed for the clock enable command. Any enabled divider can be used as reference. This allows all dividers to be aligned with each other, even when they are enabled at different times. If PA_DIV_SEL is '255' and PA_TYPE_SEL is '3', 'clk_pclk_root[i]' is used as reference.

Bits	Name	SW	HW	Default or Enum	Description
24:25	PA_TYPE_SEL	RW	RW	3	Specifies the divider type of the divider to which phase alignment is performed for the clock enable command: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers.
30	DISABLE	RW	RW	0	Clock divider disable command (mutually exclusive with ENABLE). SW sets this field to '1' and HW sets this field to '0'. The DIV_SEL and TYPE_SEL fields specify which divider is to be disabled. The HW sets the DISABLE field to '0' immediately and the HW sets the DIV_XXX_CTL.EN field of the divider to '0' immediately.
31	ENABLE	RW	RW	0	Clock divider enable command (mutually exclusive with DISABLE). Typically, SW sets this field to '1' to enable a divider and HW sets this field to '0' to indicate that divider enabling has completed. When a divider is enabled, its integer and fractional (if present) counters are initialized to '0'. If a divider is to be re-enabled using different integer and fractional divider values, the SW should follow these steps: 0: Disable the divider using the DIV_CMD.DISABLE field. 1: Configure the divider's DIV_XXX_CTL register. 2: Enable the divider using the DIV_CMD_ENABLE field. The DIV_SEL and TYPE_SEL fields specify which divider is to be enabled. The enabled divider may be phase aligned to either 'clk_pclk_root[i]' (typical usage) or to ANY enabled divider. The PA_DIV_SEL and PA_TYPE_SEL fields specify the reference divider. The HW sets the ENABLE field to '0' when the enabling is performed and the HW set the DIV_XXX_CTL.EN field of the divider to '1' when the enabling is performed. Note that enabling with phase alignment to a low frequency divider takes time. E.g. To align to a divider that generates a clock of 'clk_pclk_root[i]/n (with n being the integer divider value INT_DIV+1), up to n cycles may be required to perform alignment. Phase alignment to 'clk_pclk_root[i]' takes affect immediately. SW can set this field to '0' during phase alignment to abort the enabling process.

22.3.1.2 PERI_PCLK_GR_CLOCK_CTL

Description: Clock control
Address: 0x40040C00
Offset: 0xC00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3FF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DIV_SEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						TYPE_SEL [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DIV_SEL	RW	RW	255	Specifies one of the dividers of the divider type specified by TYPE_SEL. If DIV_SEL is '255' and TYPE_SEL is '3' (default/reset value), no divider is specified and no clock control signal(s) are generated. When transitioning a clock between two out-of-phase dividers, spurious clock control signals may be generated for one 'clk_pclk_root[i]' cycle during this transition. These clock control signals may cause a single clock period that is smaller than any of the two divider periods. To prevent these spurious clock signals, the clock multiplexer can be disconnected (DIV_SEL is '255' and TYPE_SEL is '3') for a transition time that is larger than the smaller of the two divider periods.
8:9	TYPE_SEL	RW	RW	3	Specifies divider type: 0: 8.0 (integer) clock dividers. 1: 16.0 (integer) clock dividers. 2: 16.5 (fractional) clock dividers. 3: 24.5 (fractional) clock dividers.

22.3.1.3 PERI_PCLK_GR_DIV_8_CTL

Description: Divider control (for 8.0 divider)
Address: 0x40041000
Offset: 0x1000
Retention: Retained
IsDeepSleep: No
Comment: Smallest of the divider types.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	INT8_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EN	R	R	0	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result on a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode.
8:15	INT8_DIV	RW	RW	0	Integer division by (1+INT8_DIV). Allows for integer divisions in the range [1, 256]. Note: this type of divider does NOT allow for a fractional division. For the generation of a divided clock, the integer division range is restricted to [2, 256]. For the generation of a 50/50 percent duty cycle digital divided clock, the integer division range is restricted to even numbers in the range [2, 256]. The generation of a 50/50 percent duty cycle analog divided clock has no restrictions. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

22.3.1.4 PERI_PCLK_GR_DIV_16_CTL

Description: Divider control (for 16.0 divider)
Address: 0x40041400
Offset: 0x1400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	INT16_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INT16_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EN	R	R	0	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result on a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode.
8:23	INT16_DIV	RW	RW	0	Integer division by (1+INT16_DIV). Allows for integer divisions in the range [1, 65,536]. Note: this type of divider does NOT allow for a fractional division. For the generation of a divided clock, the integer division range is restricted to [2, 65,536]. For the generation of a 50/50 percent duty cycle digital divided clock, the integer division range is restricted to even numbers in the range [2, 65,536]. The generation of a 50/50 percent duty cycle analog divided clock has no restrictions. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

22.3.1.5 PERI_PCLK_GR_DIV_24_5_CTL

Description: Divider control (for 24.5 divider)
Address: 0x40041C00
Offset: 0x1C00
Retention: Retained
IsDeepSleep: No
Comment: Largest of the divider types.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FRAC5_DIV [7:3]					None [2:1]		EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	INT24_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INT24_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INT24_DIV [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EN	R	R	0	Divider enabled. HW sets this field to '1' as a result of an ENABLE command. HW sets this field to '0' as a result on a DISABLE command. Note that this field is retained. As a result, the divider does NOT have to be re-enabled after transitioning from DeepSleep to Active power mode.
3:7	FRAC5_DIV	RW	RW	0	Fractional division by (FRAC5_DIV/32). Allows for fractional divisions in the range [0, 31/32]. Note that fractional division results in clock jitter as some clock periods may be 1 'clk_pclk_root[i]' cycle longer than other clock periods. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.
8:31	INT24_DIV	RW	RW	0	Integer division by (1+INT24_DIV). Allows for integer divisions in the range [1, 16,777,216]. Note: combined with fractional division, this divider type allows for a division in the range [1, 16,777,216 31/32] in 1/32 increments. For the generation of a divided clock, the integer division range is restricted to [2, 16,777,216 31/32]. For the generation of a 50/50 percent duty cycle divided clock, the division range is restricted to [2, 16,777,216]. Note that this field is retained. However, the counter that is used to implement the division is not and will be initialized by HW to '0' when transitioning from DeepSleep to Active power mode.

23 PROT

Description	Protection
Base Address	0x40230000
Size	0x10000
Slave Num	MMIO2 - 3

23.1 SMPU

Register Name	Address	Permission	Description
PROT_SMPU_MS0_CTL	0x40230000	FULL	Master 0 protection context control
PROT_SMPU_MS1_CTL	0x40230004	FULL	Master 1 protection context control <i>Note: P NS PC_MASK_15_TO_1 are not available for this register</i>
PROT_SMPU_MS2_CTL	0x40230008	FULL	Master 2 protection context control <i>Note: P NS PC_MASK_15_TO_1 are not available for this register</i>
PROT_SMPU_MS3_CTL	0x4023000C	FULL	Master 3 protection context control <i>Note: P NS PC_MASK_15_TO_1 are not available for this register</i>
PROT_SMPU_MS4_CTL	0x40230010	FULL	Master 4 protection context control <i>Note: P NS PC_MASK_15_TO_1 are not available for this register</i>
PROT_SMPU_MS5_CTL	0x40230014	FULL	Master 5 protection context control
PROT_SMPU_MS6_CTL	0x40230018	FULL	Master 6 protection context control
PROT_SMPU_MS13_CTL	0x40230034	FULL	Master 13 protection context control
PROT_SMPU_MS14_CTL	0x40230038	FULL	Master 14 protection context control
PROT_SMPU_MS15_CTL	0x4023003C	FULL	Master 15 protection context control

23.1.1 SMPU_STRUCT 0

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT0_ADDR0	0x40232000	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT0_ATT0	0x40232004	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT0_ADDR1	0x40232020	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT0_ATT1	0x40232024	FULL	SMPU region attributes 1 (master structure)

23.1.2 SMPU_STRUCT 1

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT1_ADDR0	0x40232040	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT1_ATT0	0x40232044	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT1_ADDR1	0x40232060	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT1_ATT1	0x40232064	FULL	SMPU region attributes 1 (master structure)

23.1.3 SMPU_STRUCT 2

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT2_ADDR0	0x40232080	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT2_ATT0	0x40232084	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT2_ADDR1	0x402320A0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT2_ATT1	0x402320A4	FULL	SMPU region attributes 1 (master structure)

23.1.4 SMPU_STRUCT 3

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT3_ADDR0	0x402320C0	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT3_ATT0	0x402320C4	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT3_ADDR1	0x402320E0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT3_ATT1	0x402320E4	FULL	SMPU region attributes 1 (master structure)

23.1.5 SMPU_STRUCT 4

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT4_ADDR0	0x40232100	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT4_ATT0	0x40232104	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT4_ADDR1	0x40232120	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT4_ATT1	0x40232124	FULL	SMPU region attributes 1 (master structure)

23.1.6 SMPU_STRUCT 5

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT5_ADDR0	0x40232140	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT5_ATT0	0x40232144	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT5_ADDR1	0x40232160	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT5_ATT1	0x40232164	FULL	SMPU region attributes 1 (master structure)

23.1.7 SMPU_STRUCT 6

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT6_ADDR0	0x40232180	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT6_ATT0	0x40232184	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT6_ADDR1	0x402321A0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT6_ATT1	0x402321A4	FULL	SMPU region attributes 1 (master structure)

23.1.8 SMPU_STRUCT 7

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT7_ADDR0	0x402321C0	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT7_ATT0	0x402321C4	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT7_ADDR1	0x402321E0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT7_ATT1	0x402321E4	FULL	SMPU region attributes 1 (master structure)

23.1.9 SMPU_STRUCT 8

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT8_ADDR0	0x40232200	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT8_ATT0	0x40232204	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT8_ADDR1	0x40232220	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT8_ATT1	0x40232224	FULL	SMPU region attributes 1 (master structure)

23.1.10 SMPU_STRUCT 9

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT9_ADDR0	0x40232240	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT9_ATT0	0x40232244	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT9_ADDR1	0x40232260	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT9_ATT1	0x40232264	FULL	SMPU region attributes 1 (master structure)

23.1.11 SMPU_STRUCT 10

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT10_ADDR0	0x40232280	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT10_ATT0	0x40232284	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT10_ADDR1	0x402322A0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT10_ATT1	0x402322A4	FULL	SMPU region attributes 1 (master structure)

23.1.12 SMPU_STRUCT 11

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT11_ADDR0	0x402322C0	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT11_ATT0	0x402322C4	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT11_ADDR1	0x402322E0	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT11_ATT1	0x402322E4	FULL	SMPU region attributes 1 (master structure)

23.1.13 SMPU_STRUCT 12

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT12_ADDR0	0x40232300	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT12_ATT0	0x40232304	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT12_ADDR1	0x40232320	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT12_ATT1	0x40232324	FULL	SMPU region attributes 1 (master structure)

23.1.14 SMPU_STRUCT 13

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT13_ADDR0	0x40232340	FULL	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT13_ATT0	0x40232344	FULL	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT13_ADDR1	0x40232360	FULL	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT13_ATT1	0x40232364	FULL	SMPU region attributes 1 (master structure)

23.1.15 SMPU_STRUCT 14

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT14_ADDR0	0x40232380	SECURE - READ	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT14_ATT0	0x40232384	SECURE - READ	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT14_ADDR1	0x402323A0	SECURE - READ	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT14_ATT1	0x402323A4	SECURE - READ	SMPU region attributes 1 (master structure)

23.1.16 SMPU_STRUCT 15

Register Name	Address	Permission	Description
PROT_SMPU_SMPU_STRUCT15_ADDR0	0x402323C0	SECURE - READ	SMPU region address 0 (slave structure)
PROT_SMPU_SMPU_STRUCT15_ATT0	0x402323C4	SECURE - READ	SMPU region attributes 0 (slave structure)
PROT_SMPU_SMPU_STRUCT15_ADDR1	0x402323E0	SECURE - READ	SMPU region address 1 (master structure)
PROT_SMPU_SMPU_STRUCT15_ATT1	0x402323E4	SECURE - READ	SMPU region attributes 1 (master structure)

23.2 MPU 0

Register Name	Address	Permission	Description
PROT_MPU0_MS_CTL	0x40234000	FULL	Master control
PROT_MPU0_MS_CTL_READ_MIR0	0x40234004	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR1	0x40234008	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR2	0x4023400C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR3	0x40234010	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR4	0x40234014	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR5	0x40234018	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR6	0x4023401C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR7	0x40234020	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR8	0x40234024	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR9	0x40234028	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR10	0x4023402C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR11	0x40234030	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR12	0x40234034	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR13	0x40234038	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR14	0x4023403C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR15	0x40234040	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR16	0x40234044	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR17	0x40234048	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR18	0x4023404C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR19	0x40234050	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR20	0x40234054	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR21	0x40234058	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR22	0x4023405C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR23	0x40234060	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR24	0x40234064	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR25	0x40234068	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR26	0x4023406C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR27	0x40234070	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR28	0x40234074	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR29	0x40234078	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR30	0x4023407C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR31	0x40234080	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR32	0x40234084	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR33	0x40234088	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR34	0x4023408C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR35	0x40234090	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR36	0x40234094	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR37	0x40234098	FULL	Master control read mirror

Technical Reference Manual	1849	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
PROT_MPU0_MS_CTL_READ_MIR101	0x40234198	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR102	0x4023419C	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR103	0x402341A0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR104	0x402341A4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR105	0x402341A8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR106	0x402341AC	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR107	0x402341B0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR108	0x402341B4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR109	0x402341B8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR110	0x402341BC	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR111	0x402341C0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR112	0x402341C4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR113	0x402341C8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR114	0x402341CC	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR115	0x402341D0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR116	0x402341D4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR117	0x402341D8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR118	0x402341DC	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR119	0x402341E0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR120	0x402341E4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR121	0x402341E8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR122	0x402341EC	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR123	0x402341F0	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR124	0x402341F4	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR125	0x402341F8	FULL	Master control read mirror
PROT_MPU0_MS_CTL_READ_MIR126	0x402341FC	FULL	Master control read mirror

23.3 MPU 5

Register Name	Address	Permission	Description
PROT_MPU5_MS_CTL	0x40235400	FULL	Master control Note: PC_SAVED is not available for this register
PROT_MPU5_MS_CTL_READ_MIR0	0x40235404	FULL	Master control read mirror Note: PC_SAVED is not available for this register
PROT_MPU5_MS_CTL_READ_MIR1	0x40235408	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR2	0x4023540C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR3	0x40235410	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR4	0x40235414	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR5	0x40235418	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR6	0x4023541C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR7	0x40235420	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR8	0x40235424	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR9	0x40235428	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR10	0x4023542C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR11	0x40235430	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR12	0x40235434	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR13	0x40235438	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR14	0x4023543C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR15	0x40235440	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR16	0x40235444	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR17	0x40235448	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR18	0x4023544C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR19	0x40235450	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR20	0x40235454	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR21	0x40235458	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR22	0x4023545C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR23	0x40235460	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR24	0x40235464	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR25	0x40235468	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR26	0x4023546C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR27	0x40235470	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR28	0x40235474	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR29	0x40235478	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR30	0x4023547C	FULL	Master control read mirror

Technical Reference Manual	1851	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
PROT_MPU5_MS_CTL_READ_MIR94	0x4023557C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR95	0x40235580	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR96	0x40235584	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR97	0x40235588	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR98	0x4023558C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR99	0x40235590	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR100	0x40235594	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR101	0x40235598	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR102	0x4023559C	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR103	0x402355A0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR104	0x402355A4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR105	0x402355A8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR106	0x402355AC	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR107	0x402355B0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR108	0x402355B4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR109	0x402355B8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR110	0x402355BC	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR111	0x402355C0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR112	0x402355C4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR113	0x402355C8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR114	0x402355CC	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR115	0x402355D0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR116	0x402355D4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR117	0x402355D8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR118	0x402355DC	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR119	0x402355E0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR120	0x402355E4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR121	0x402355E8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR122	0x402355EC	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR123	0x402355F0	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR124	0x402355F4	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR125	0x402355F8	FULL	Master control read mirror
PROT_MPU5_MS_CTL_READ_MIR126	0x402355FC	FULL	Master control read mirror

23.3.1 MPU_STRUCT 0

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT0_ADDR	0x40235600	FULL	MPU region address
PROT_MPU5_MPU_STRUCT0_ATT	0x40235604	FULL	MPU region attributes

23.3.2 MPU_STRUCT 1

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT1_ADDR	0x40235620	FULL	MPU region address
PROT_MPU5_MPU_STRUCT1_ATT	0x40235624	FULL	MPU region attributes

23.3.3 MPU_STRUCT 2

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT2_ADDR	0x40235640	FULL	MPU region address
PROT_MPU5_MPU_STRUCT2_ATT	0x40235644	FULL	MPU region attributes

23.3.4 MPU_STRUCT 3

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT3_ADDR	0x40235660	FULL	MPU region address
PROT_MPU5_MPU_STRUCT3_ATT	0x40235664	FULL	MPU region attributes

23.3.5 MPU_STRUCT 4

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT4_ADDR	0x40235680	FULL	MPU region address
PROT_MPU5_MPU_STRUCT4_ATT	0x40235684	FULL	MPU region attributes

23.3.6 MPU_STRUCT 5

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT5_ADDR	0x402356A0	FULL	MPU region address
PROT_MPU5_MPU_STRUCT5_ATT	0x402356A4	FULL	MPU region attributes

23.3.7 MPU_STRUCT 6

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT6_ADDR	0x402356C0	FULL	MPU region address
PROT_MPU5_MPU_STRUCT6_ATT	0x402356C4	FULL	MPU region attributes

23.3.8 MPU_STRUCT 7

Register Name	Address	Permission	Description
PROT_MPU5_MPU_STRUCT7_ADDR	0x402356E0	FULL	MPU region address
PROT_MPU5_MPU_STRUCT7_ATT	0x402356E4	FULL	MPU region attributes

23.4 MPU 6

Register Name	Address	Permission	Description
PROT_MPU6_MS_CTL	0x40235800	FULL	Master control Note:PC_SAVED is not available for this register
PROT_MPU6_MS_CTL_READ_MIR0	0x40235804	FULL	Master control read mirror Note:PC_SAVED is not available for this register
PROT_MPU6_MS_CTL_READ_MIR1	0x40235808	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR2	0x4023580C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR3	0x40235810	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR4	0x40235814	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR5	0x40235818	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR6	0x4023581C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR7	0x40235820	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR8	0x40235824	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR9	0x40235828	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR10	0x4023582C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR11	0x40235830	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR12	0x40235834	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR13	0x40235838	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR14	0x4023583C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR15	0x40235840	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR16	0x40235844	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR17	0x40235848	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR18	0x4023584C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR19	0x40235850	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR20	0x40235854	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR21	0x40235858	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR22	0x4023585C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR23	0x40235860	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR24	0x40235864	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR25	0x40235868	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR26	0x4023586C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR27	0x40235870	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR28	0x40235874	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR29	0x40235878	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR30	0x4023587C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR31	0x40235880	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR32	0x40235884	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR33	0x40235888	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR34	0x4023588C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR35	0x40235890	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR36	0x40235894	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR37	0x40235898	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR38	0x4023589C	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR39	0x402358A0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR40	0x402358A4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR41	0x402358A8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR42	0x402358AC	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR43	0x402358B0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR44	0x402358B4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR45	0x402358B8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR46	0x402358BC	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR47	0x402358C0	FULL	Master control read mirror

Technical Reference Manual 1854 002-33817 Rev. **
2021-10-22

Register Name	Address	Permission	Description
PROT_MPU6_MS_CTL_READ_MIR111	0x402359C0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR112	0x402359C4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR113	0x402359C8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR114	0x402359CC	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR115	0x402359D0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR116	0x402359D4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR117	0x402359D8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR118	0x402359DC	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR119	0x402359E0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR120	0x402359E4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR121	0x402359E8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR122	0x402359EC	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR123	0x402359F0	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR124	0x402359F4	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR125	0x402359F8	FULL	Master control read mirror
PROT_MPU6_MS_CTL_READ_MIR126	0x402359FC	FULL	Master control read mirror

23.4.1 MPU_STRUCT 0

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT0_ADDR	0x40235A00	FULL	MPU region address
PROT_MPU6_MPU_STRUCT0_ATT	0x40235A04	FULL	MPU region attributes

23.4.2 MPU_STRUCT 1

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT1_ADDR	0x40235A20	FULL	MPU region address
PROT_MPU6_MPU_STRUCT1_ATT	0x40235A24	FULL	MPU region attributes

23.4.3 MPU_STRUCT 2

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT2_ADDR	0x40235A40	FULL	MPU region address
PROT_MPU6_MPU_STRUCT2_ATT	0x40235A44	FULL	MPU region attributes

23.4.4 MPU_STRUCT 3

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT3_ADDR	0x40235A60	FULL	MPU region address
PROT_MPU6_MPU_STRUCT3_ATT	0x40235A64	FULL	MPU region attributes

23.4.5 MPU_STRUCT 4

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT4_ADDR	0x40235A80	FULL	MPU region address
PROT_MPU6_MPU_STRUCT4_ATT	0x40235A84	FULL	MPU region attributes

23.4.6 MPU_STRUCT 5

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT5_ADDR	0x40235AA0	FULL	MPU region address
PROT_MPU6_MPU_STRUCT5_ATT	0x40235AA4	FULL	MPU region attributes

23.4.7 MPU_STRUCT 6

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT6_ADDR	0x40235AC0	FULL	MPU region address
PROT_MPU6_MPU_STRUCT6_ATT	0x40235AC4	FULL	MPU region attributes

23.4.8 MPU_STRUCT 7

Register Name	Address	Permission	Description
PROT_MPU6_MPU_STRUCT7_ADDR	0x40235AE0	FULL	MPU region address
PROT_MPU6_MPU_STRUCT7_ATT	0x40235AE4	FULL	MPU region attributes

23.5 MPU 13

Register Name	Address	Permission	Description
PROT_MPU13_MS_CTL	0x40237400	FULL	Master control Note: PC_SAVED is not available for this register

Register Name	Address	Permission	Description
PROT_MPU13_MS_CTL_READ_MIR0	0x40237404	FULL	Master control read mirror Note: PC_SAVED is not available for this register
PROT_MPU13_MS_CTL_READ_MIR1	0x40237408	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR2	0x4023740C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR3	0x40237410	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR4	0x40237414	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR5	0x40237418	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR6	0x4023741C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR7	0x40237420	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR8	0x40237424	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR9	0x40237428	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR10	0x4023742C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR11	0x40237430	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR12	0x40237434	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR13	0x40237438	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR14	0x4023743C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR15	0x40237440	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR16	0x40237444	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR17	0x40237448	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR18	0x4023744C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR19	0x40237450	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR20	0x40237454	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR21	0x40237458	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR22	0x4023745C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR23	0x40237460	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR24	0x40237464	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR25	0x40237468	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR26	0x4023746C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR27	0x40237470	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR28	0x40237474	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR29	0x40237478	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR30	0x4023747C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR31	0x40237480	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR32	0x40237484	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR33	0x40237488	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR34	0x4023748C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR35	0x40237490	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR36	0x40237494	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR37	0x40237498	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR38	0x4023749C	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR39	0x402374A0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR40	0x402374A4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR41	0x402374A8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR42	0x402374AC	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR43	0x402374B0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR44	0x402374B4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR45	0x402374B8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR46	0x402374BC	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR47	0x402374C0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR48	0x402374C4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR49	0x402374C8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR50	0x402374CC	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR51	0x402374D0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR52	0x402374D4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR53	0x402374D8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR54	0x402374DC	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR55	0x402374E0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR56	0x402374E4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR57	0x402374E8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR58	0x402374EC	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR59	0x402374F0	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR60	0x402374F4	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR61	0x402374F8	FULL	Master control read mirror

Technical Reference Manual	1857	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
PROT_MPU13_MS_CTL_READ_MIR125	0x402375F8	FULL	Master control read mirror
PROT_MPU13_MS_CTL_READ_MIR126	0x402375FC	FULL	Master control read mirror

23.6 MPU 14

Register Name	Address	Permission	Description
PROT_MPU14_MS_CTL	0x40237800	FULL	Master control Note:PC_SAVED is not available for this register
PROT_MPU14_MS_CTL_READ_MIR0	0x40237804	FULL	Master control read mirror Note:PC_SAVED is not available for this register
PROT_MPU14_MS_CTL_READ_MIR1	0x40237808	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR2	0x4023780C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR3	0x40237810	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR4	0x40237814	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR5	0x40237818	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR6	0x4023781C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR7	0x40237820	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR8	0x40237824	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR9	0x40237828	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR10	0x4023782C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR11	0x40237830	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR12	0x40237834	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR13	0x40237838	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR14	0x4023783C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR15	0x40237840	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR16	0x40237844	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR17	0x40237848	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR18	0x4023784C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR19	0x40237850	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR20	0x40237854	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR21	0x40237858	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR22	0x4023785C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR23	0x40237860	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR24	0x40237864	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR25	0x40237868	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR26	0x4023786C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR27	0x40237870	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR28	0x40237874	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR29	0x40237878	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR30	0x4023787C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR31	0x40237880	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR32	0x40237884	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR33	0x40237888	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR34	0x4023788C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR35	0x40237890	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR36	0x40237894	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR37	0x40237898	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR38	0x4023789C	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR39	0x402378A0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR40	0x402378A4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR41	0x402378A8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR42	0x402378AC	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR43	0x402378B0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR44	0x402378B4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR45	0x402378B8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR46	0x402378BC	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR47	0x402378C0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR48	0x402378C4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR49	0x402378C8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR50	0x402378CC	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR51	0x402378D0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR52	0x402378D4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR53	0x402378D8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR54	0x402378DC	FULL	Master control read mirror

Technical Reference Manual	1859	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
PROT_MPU14_MS_CTL_READ_MIR118	0x402379DC	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR119	0x402379E0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR120	0x402379E4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR121	0x402379E8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR122	0x402379EC	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR123	0x402379F0	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR124	0x402379F4	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR125	0x402379F8	FULL	Master control read mirror
PROT_MPU14_MS_CTL_READ_MIR126	0x402379FC	FULL	Master control read mirror

23.7 MPU 15

Register Name	Address	Permission	Description
PROT_MPU15_MS_CTL	0x40237C00	FULL	Master control Note:PC_SAVED is not available for this register
PROT_MPU15_MS_CTL_READ_MIR0	0x40237C04	FULL	Master control read mirror Note:PC_SAVED is not available for this register
PROT_MPU15_MS_CTL_READ_MIR1	0x40237C08	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR2	0x40237C0C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR3	0x40237C10	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR4	0x40237C14	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR5	0x40237C18	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR6	0x40237C1C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR7	0x40237C20	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR8	0x40237C24	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR9	0x40237C28	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR10	0x40237C2C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR11	0x40237C30	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR12	0x40237C34	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR13	0x40237C38	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR14	0x40237C3C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR15	0x40237C40	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR16	0x40237C44	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR17	0x40237C48	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR18	0x40237C4C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR19	0x40237C50	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR20	0x40237C54	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR21	0x40237C58	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR22	0x40237C5C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR23	0x40237C60	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR24	0x40237C64	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR25	0x40237C68	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR26	0x40237C6C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR27	0x40237C70	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR28	0x40237C74	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR29	0x40237C78	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR30	0x40237C7C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR31	0x40237C80	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR32	0x40237C84	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR33	0x40237C88	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR34	0x40237C8C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR35	0x40237C90	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR36	0x40237C94	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR37	0x40237C98	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR38	0x40237C9C	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR39	0x40237CA0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR40	0x40237CA4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR41	0x40237CA8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR42	0x40237CAC	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR43	0x40237CB0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR44	0x40237CB4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR45	0x40237CB8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR46	0x40237CBC	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR47	0x40237CC0	FULL	Master control read mirror

Technical Reference Manual	1861	002-33817 Rev. ** 2021-10-22

Register Name	Address	Permission	Description
PROT_MPU15_MS_CTL_READ_MIR111	0x40237DC0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR112	0x40237DC4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR113	0x40237DC8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR114	0x40237DCC	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR115	0x40237DD0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR116	0x40237DD4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR117	0x40237DD8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR118	0x40237DDC	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR119	0x40237DE0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR120	0x40237DE4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR121	0x40237DE8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR122	0x40237DEC	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR123	0x40237DF0	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR124	0x40237DF4	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR125	0x40237DF8	FULL	Master control read mirror
PROT_MPU15_MS_CTL_READ_MIR126	0x40237DFC	FULL	Master control read mirror

23.7.1 MPU_STRUCT 0

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT0_ADDR	0x40237E00	FULL	MPU region address
PROT_MPU15_MPU_STRUCT0_ATT	0x40237E04	FULL	MPU region attributes

23.7.2 MPU_STRUCT 1

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT1_ADDR	0x40237E20	FULL	MPU region address
PROT_MPU15_MPU_STRUCT1_ATT	0x40237E24	FULL	MPU region attributes

23.7.3 MPU_STRUCT 2

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT2_ADDR	0x40237E40	FULL	MPU region address
PROT_MPU15_MPU_STRUCT2_ATT	0x40237E44	FULL	MPU region attributes

23.7.4 MPU_STRUCT 3

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT3_ADDR	0x40237E60	FULL	MPU region address
PROT_MPU15_MPU_STRUCT3_ATT	0x40237E64	FULL	MPU region attributes

23.7.5 MPU_STRUCT 4

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT4_ADDR	0x40237E80	FULL	MPU region address
PROT_MPU15_MPU_STRUCT4_ATT	0x40237E84	FULL	MPU region attributes

23.7.6 MPU_STRUCT 5

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT5_ADDR	0x40237EA0	FULL	MPU region address
PROT_MPU15_MPU_STRUCT5_ATT	0x40237EA4	FULL	MPU region attributes

23.7.7 MPU_STRUCT 6

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT6_ADDR	0x40237EC0	FULL	MPU region address
PROT_MPU15_MPU_STRUCT6_ATT	0x40237EC4	FULL	MPU region attributes

23.7.8 MPU_STRUCT 7

Register Name	Address	Permission	Description
PROT_MPU15_MPU_STRUCT7_ADDR	0x40237EE0	FULL	MPU region address
PROT_MPU15_MPU_STRUCT7_ATT	0x40237EE4	FULL	MPU region attributes

23.8 Register Details

23.8.1 SMPU

23.8.1.1 PROT_SMPU_MS0_CTL

Description: Master 0 protection context control

Address: 0x40230000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: Each master has an associated SMPU MS_CTL register. This register provides master specific information. In a system with a secure entity, this register is typically only accessible by the secure entity, to prevent a master from changing its own privileged setting, security setting, arbitration priority or enabled protection contexts.
 Master 0 (CM0+ processor) uses SMPU MS0_CTL.
 Master 1 (cryptography IP) uses SMPU MS1_CTL.
 Master 2 (DataWire 0) uses SMPU MS2_CTL.
 Master 3 (DataWire 1) uses SMPU MS3_CTL.

....

Master 14 (CM4 processor) uses SMPU MS14_CTL.

Master 15 (test controller) uses SMPU MS15_CTL.

Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	Privileged setting ('0': user mode; '1': privileged mode). Notes: This field is ONLY used for masters that do NOT provide their own user/privileged access control attribute. The default/reset field value provides privileged mode access capabilities.
1	NS	RW	RW	1	Security setting ('0': secure mode; '1': non-secure mode). Notes: This field is ONLY used for masters that do NOT provide their own secure/non-secure access control attribute. Note that the default/reset field value provides non-secure mode access capabilities to all masters.

Bits	Name	SW	HW	Default or Enum	Description
8:9	PRI0	RW	RW	3	Device wide bus arbitration priority setting ('0': highest priority, '3': lowest priority). Notes: The AHB-Lite interconnect performs arbitration on the individual beats/transfers of a burst (this optimizes latency over locality/bandwidth). The AXI-Lite interconnects performs a single arbitration for the complete burst (this optimizes locality/bandwidth over latency). Masters with the same priority setting form a 'priority group'. Within a 'priority group', round robin arbitration is performed.
16	PC_MASK_0	R	R	0	Protection context mask for protection context '0'. This field is a constant '0': - PC_MASK_0 is '0': MPU MS_CTL.PC[3:0] can NOT be set to '0' and PC[3:0] is not changed. If the protection context of the write transfer is '0', protection is not applied and PC[3:0] can be changed.
17:31	PC_MASK_15_TO_1	RW	RW	0	Protection context mask for protection contexts '15' down to '1'. Bit PC_MASK_15_TO_1[i] indicates if the MPU MS_CTL.PC[3:0] protection context field can be set to the value 'i+1': - PC_MASK_15_TO_1[i] is '0': MPU MS_CTL.PC[3:0] can NOT be set to 'i+1'; and PC[3:0] is not changed. If the protection context of the write transfer is '0', protection is not applied and PC[3:0] can be changed. - PC_MASK_15_TO_1[i] is '1': MPU MS_CTL.PC[3:0] can be set to 'i+1'. Note: When CPUSS_CM0_PC_CTL.VALID[i] is '1' (the associated protection context handler is valid), write transfers to PC_MASK_15_TO_1[i-1] always write '0', regardless of data written. This ensures that when valid protection context handlers are used to enter protection contexts 1, 2 or 3 through (HW modifies MPU MS_CTL.PC[3:0] on entry of the handler), it is NOT possible for SW to enter those protection contexts (SW modifies MPU MS_CTL.PC[3:0]).

23.8.1.2 PROT_SMPU_MS1_CTL

Description: Master 1 protection context control
Address: 0x40230004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.3 PROT_SMPU_MS2_CTL

Description: Master 2 protection context control
Address: 0x40230008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.4 PROT_SMPU_MS3_CTL

Description: Master 3 protection context control
Address: 0x4023000C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.5 PROT_SMPU_MS4_CTL

Description: Master 4 protection context control
Address: 0x40230010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.6 PROT_SMPU_MS5_CTL

Description: Master 5 protection context control
Address: 0x40230014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.7 PROT_SMPU_MS6_CTL

Description: Master 6 protection context control
Address: 0x40230018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.8 PROT_SMPU_MS13_CTL

Description: Master 13 protection context control
Address: 0x40230034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.9 PROT_SMPU_MS14_CTL

Description: Master 14 protection context control
Address: 0x40230038
Offset: 0x38
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.10 PROT_SMPU_MS15_CTL

Description: Master 15 protection context control
Address: 0x4023003C
Offset: 0x3C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x303

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						NS [1:1]	P [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						PRIO [9:8]	

Bits	23	22	21	20	19	18	17	16
Name								PC_MASK_0 [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PC_MASK_15_TO_1 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	P	RW	RW	1	See MS0_CTL.P.
1	NS	RW	RW	1	See MS0_CTL.NS.
8:9	PRIO	RW	RW	3	See MS0_CTL.PRIO
16	PC_MASK_0	R	R	0	See MS0_CTL.PC_MASK_0.
17:31	PC_MASK_15_TO_1	RW	RW	0	See MS0_CTL.PC_MASK_15_TO_1.

23.8.1.11 SMPU_STRUCT

23.8.1.11.1 PROT_SMPU_SMPU_STRUCT_ADDR0

Description: SMPU region address 0 (slave structure)
Address: 0x40232000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register defines a SMPU address region.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUBREGION_DISABLE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDR24 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDR24 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDR24 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SUBREGION_DISABLE	RW	RW	Undefined	This field is used to individually disabled the eight equally sized subregions in which a region is partitioned. Subregion disable: Bit 0: subregion 0 disable. Bit 1: subregion 1 disable. Bit 2: subregion 2 disable. Bit 3: subregion 3 disable. Bit 4: subregion 4 disable. Bit 5: subregion 5 disable. Bit 6: subregion 6 disable. Bit 7: subregion 7 disable. E.g., a 64 KByte address region (ATT0.REGION_SIZE is '15') has eight 8 KByte subregions. The access control as defined by ATT0 applies if the bus transfer address is within the address region AND the addressed subregion is NOT disabled. Note that the smallest region size is 256 B and the smallest subregion size is 32 B.
8:31	ADDR24	RW	RW	Undefined	This field specifies the most significant bits of the 32-bit address of an address region. The region size is defined by ATT0.REGION_SIZE. A region of n Byte is always n Byte aligned. As a result, some of the lesser significant address bits of ADDR24 may be ignored in determining whether a bus transfer address is within an address region. E.g., a 64 KByte address region (REGION_SIZE is '15') is 64 KByte aligned, and ADDR24[7:0] are ignored.

23.8.1.11.2 PROT_SMPU_SMPU_STRUCT_ATT0

Description: SMPU region attributes 0 (slave structure)
Address: 0x40232004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: This register defines SMPU access control.
Default: 0x100

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	NS [6:6]	PX [5:5]	PW [4:4]	PR [3:3]	UX [2:2]	UW [1:1]	UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name								PC_MASK_0 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	PC_MASK_15_TO_1 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	PC_MATCH [30:30]	None [29:29]	REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	UR	RW	RW	Undefined	User read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	UW	RW	RW	Undefined	User write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	UX	RW	RW	Undefined	User execute enable: '0': Disabled (user, execute accesses are NOT allowed). '1': Enabled (user, execute accesses are allowed).
3	PR	RW	RW	Undefined	Privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
4	PW	RW	RW	Undefined	Privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).
5	PX	RW	RW	Undefined	Privileged execute enable: '0': Disabled (privileged, execute accesses are NOT allowed). '1': Enabled (privileged, execute accesses are allowed).
6	NS	RW	RW	Undefined	Non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC_MASK_0	R	R	1	This field specifies protection context identifier based access control for protection context '0'.

Bits	Name	SW	HW	Default or Enum	Description
9:23	PC_MASK_15_TO_1	RW	RW	Undefined	This field specifies protection context identifier based access control. Bit i: protection context i+1 enable. If '0', protection context i+1 access is disabled; i.e. not allowed. If '1', protection context i+1 access is enabled; i.e. allowed.
24:28	REGION_SIZE	RW	RW	Undefined	This field specifies the region size: '0'-'6': Undefined. '7': 256 B region '8': 512 B region '9': 1 KB region '10': 2 KB region '11': 4 KB region '12': 8 KB region '13': 16 KB region '14': 32 KB region '15': 64 KB region '16': 128 KB region '17': 256 KB region '18': 512 KB region '19': 1 MB region '20': 2 MB region '21': 4 MB region '22': 8 MB region '23': 16 MB region '24': 32 MB region '25': 64 MB region '26': 128 MB region '27': 256 MB region '28': 512 MB region '29': 1 GB region '30': 2 GB region '31': 4 GB region
30	PC_MATCH	RW	RW	Undefined	This field specifies if the PC field participates in the 'matching' process or the 'access evaluation' process: '0': PC field participates in 'access evaluation'. '1': PC field participates in 'matching'. 'Matching' process. For each protection structure, the process identifies if a transfer address is contained within the address range. This identifies the 'matching' regions. 'Access evaluation' process. For each protection structure, the process evaluates the bus transfer access attributes against the access control attributes. Note that it is possible to define different access control for multiple protection contexts by using multiple protection structures with the same address region and PC_MATCH set to '1'.
31	ENABLED	RW	RW	0	Region enable: '0': Disabled. A disabled region will never result in a match on the bus transfer address. '1': Enabled. Note: a disabled address region performs logic gating to reduce dynamic power consumption.

23.8.1.11.3 PROT_SMPU_SMPU_STRUCT_ADDR1

Description: SMPU region address 1 (master structure)
Address: 0x40232020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: This register defines a SMPU address region. The address region is fixed, the region size is 64 B (two 32 B subregions within a 256 B region) and includes the ADDR0, ATT0, ADDR1 and ATT0 registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUBREGION_DISABLE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDR24 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDR24 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDR24 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SUBREGION_DISABLE	R	R	SUBREGION_DISABLE_DEF1	This field is used to individually disabled the eight equally sized subregions in which a region is partitioned. Subregion disable: Bit 0: subregion 0 disable. Bit 1: subregion 1 disable. Bit 2: subregion 2 disable. Bit 3: subregion 3 disable. Bit 4: subregion 4 disable. Bit 5: subregion 5 disable. Bit 6: subregion 6 disable. Bit 7: subregion 7 disable. Two out of a total of eight 32 B subregions are enabled. These subregions includes region structures 0 and 1. Note: this field is read-only.
8:31	ADDR24	R	R	ADDR_DEF1	This field specifies the most significant bits of the 32-bit address of an address region. 'ADDR_DEF1': base address of structure. Note: this field is read-only.

23.8.1.11.4 PROT_SMPU_SMPU_STRUCT_ATT1

Description: SMPU region attributes 1 (master structure)
Address: 0x40232024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment: This register defines SMPU access control.
Default: 0x7000109

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	NS [6:6]	PX [5:5]	PW [4:4]	PR [3:3]	UX [2:2]	UW [1:1]	UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name								PC_MASK_0 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	PC_MASK_15_TO_1 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	PC_MATCH [30:30]	None [29:29]	REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	UR	R	R	1	User read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed). Note that this register is constant '1'; i.e. user read accesses are ALWAYS allowed.
1	UW	RW	RW	Undefined	User write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	UX	R	R	0	User execute enable: '0': Disabled (user, execute accesses are NOT allowed). '1': Enabled (user, execute accesses are allowed). Note that this register is constant '0'; i.e. user execute accesses are NEVER allowed.
3	PR	R	R	1	Privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed). Note that this register is constant '1'; i.e. privileged read accesses are ALWAYS allowed.
4	PW	RW	RW	Undefined	Privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).

Bits	Name	SW	HW	Default or Enum	Description
5	PX	R	R	0	Privileged execute enable: '0': Disabled (privileged, execute accesses are NOT allowed). '1': Enabled (privileged, execute accesses are allowed). Note that this register is constant '0'; i.e. privileged execute accesses are NEVER allowed.
6	NS	RW	RW	Undefined	Non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).
8	PC_MASK_0	R	R	1	This field specifies protection context identifier based access control for protection context '0'.
9:23	PC_MASK_15_TO_1	RW	RW	Undefined	This field specifies protection context identifier based access control. Bit i: protection context i+1 enable. If '0', protection context i+1 access is disabled; i.e. not allowed. If '1', protection context i+1 access is enabled; i.e. allowed.
24:28	REGION_SIZE	R	R	7	This field specifies the region size: '7': 256 B region (8 32 B subregions) Note: this field is read-only.
30	PC_MATCH	RW	RW	Undefined	This field specifies if the PC field participates in the 'matching' process or the 'access evaluation' process: '0': PC field participates in 'access evaluation'. '1': PC field participates in 'matching'. 'Matching' process. For each protection structure, the process identifies if a transfer address is contained within the address range. This identifies the 'matching' regions. 'Access evaluation' process. For each protection structure, the process evaluates the bus transfer access attributes against the access control attributes. Note that it is possible to define different access control for multiple protection contexts by using multiple protection structures with the same address region and PC_MATCH set to '1'.
31	ENABLED	RW	RW	0	Region enable: '0': Disabled. A disabled region will never result in a match on the bus transfer address. '1': Enabled.

23.8.2 MPU

23.8.2.1 PROT_MPU_MS_CTL

Description: Master control
Address: 0x40234000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				PC [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				PC_SAVED [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PC	RW	RW	0	Active protection context (PC). Modifications to this field are constrained by the associated SMPU MS_CTL.PC_MASK_0 and MS_CTL.PC_MASK_15_TO_1[] fields. In addition, a write transfer with protection context '0' can change this field (protection context 0 has unrestricted access). The CM0+ MPU MS_CTL register is special: the PC field is modifiable by BOTH HW and SW (for all other masters, the MPU MS_CTL.PC field is modifiable by SW ONLY. For CM0+ PC field HW modifications, the following holds: * On entry of a CM0_PC0/1/2/3_HANDLER exception/interrupt handler: IF (the new PC is the same as MS_CTL.PC) PC is not affected; PC_SAVED is not affected. ELSE IF (CM0_PC_CTL.VALID[MS_CTL.PC]) An AHB-Lite bus error is generated for the exception handler fetch; PC is not affected; PC_SAVED is not affected. ELSE PC = 'new PC'; PC_SAVED = PC (push operation). * On entry of any other exception/interrupt handler: PC = PC_SAVED; PC_SAVED is not affected (pop operation). Note that the CM0_PC0/1/2/3_HANDLER and CM0_PC_CTL registers are part of repetitive CPUSS MMIO registers. Note: this field is NOT used by the DW controllers, DMA controller, AXI DMA controller, CRYPTO component and VIDEOSS.

Bits	Name	SW	HW	Default or Enum	Description
16:19	PC_SAVED	RW	RW	0	Saved protection context. Modifications to this field are constrained by the associated S MPU MS_CTL.PC_MASK_0 and MS_CTL.PC_MASK_15_TO_1[] fields. Note: this field is ONLY used by the CM0+.

23.8.2.2 PROT_MPU_MS_CTL_READ_MIR

Description: Master control read mirror
Address: 0x40234004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				PC [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				PC_SAVED [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PC	R	R	0	Read-only mirror of MS_CTL.PC
16:19	PC_SAVED	R	R	0	Read-only mirror of MS_CTL.PC_SAVED

23.8.2.3 MPU_STRUCT

23.8.2.3.1 PROT_MPU_MPU_STRUCT_ADDR

Description: MPU region address
Address: 0x40234200
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register defines a MPU address region.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SUBREGION_DISABLE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADDR24 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADDR24 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADDR24 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SUBREGION_DISABLE	RW	RW	Undefined	This field is used to individually disabled the eight equally sized subregions in which a region is partitioned. Subregion disable: Bit 0: subregion 0 disable. Bit 1: subregion 1 disable. Bit 2: subregion 2 disable. Bit 3: subregion 3 disable. Bit 4: subregion 4 disable. Bit 5: subregion 5 disable. Bit 6: subregion 6 disable. Bit 7: subregion 7 disable. E.g., a 64 KByte address region (REGION_SIZE is '15') has eight 8 KByte subregions. The access control as defined by MPU_REGION_ATT applies if the bus transfer address is within the address region AND the addressed subregion is NOT disabled. Note that the smallest region size is 256 B and the smallest subregion size is 32 B.
8:31	ADDR24	RW	RW	Undefined	This field specifies the most significant bits of the 32-bit address of an address region. The region size is defined by ATT.REGION_SIZE. A region of n Byte is always n Byte aligned. As a result, some of the lesser significant address bits of ADDR24 may be ignored in determining whether a bus transfer address is within an address region. E.g., a 64 KByte address region (REGION_SIZE is '15') is 64 KByte aligned, and ADDR24[7:0] are ignored.

23.8.2.3.2 PROT_MPU_MPU_STRUCT_ATT

Description: MPU region attributes
Address: 0x40234204
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: This register defines a MPU access control register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	NS [6:6]	PX [5:5]	PW [4:4]	PR [3:3]	UX [2:2]	UW [1:1]	UR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:29]		REGION_SIZE [28:24]				

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	UR	RW	RW	Undefined	User read enable: '0': Disabled (user, read accesses are NOT allowed). '1': Enabled (user, read accesses are allowed).
1	UW	RW	RW	Undefined	User write enable: '0': Disabled (user, write accesses are NOT allowed). '1': Enabled (user, write accesses are allowed).
2	UX	RW	RW	Undefined	User execute enable: '0': Disabled (user, execute accesses are NOT allowed). '1': Enabled (user, execute accesses are allowed).
3	PR	RW	RW	Undefined	Privileged read enable: '0': Disabled (privileged, read accesses are NOT allowed). '1': Enabled (privileged, read accesses are allowed).
4	PW	RW	RW	Undefined	Privileged write enable: '0': Disabled (privileged, write accesses are NOT allowed). '1': Enabled (privileged, write accesses are allowed).
5	PX	RW	RW	Undefined	Privileged execute enable: '0': Disabled (privileged, execute accesses are NOT allowed). '1': Enabled (privileged, execute accesses are allowed).
6	NS	RW	RW	Undefined	Non-secure: '0': Secure (secure accesses allowed, non-secure access NOT allowed). '1': Non-secure (both secure and non-secure accesses allowed).

Bits	Name	SW	HW	Default or Enum	Description
24:28	REGION_SIZE	RW	RW	Undefined	This field specifies the region size: '0'-'6': Undefined. '7': 256 B region '8': 512 B region '9': 1 KB region '10': 2 KB region '11': 4 KB region '12': 8 KB region '13': 16 KB region '14': 32 KB region '15': 64 KB region '16': 128 KB region '17': 256 KB region '18': 512 KB region '19': 1 MB region '20': 2 MB region '21': 4 MB region '22': 8 MB region '23': 16 MB region '24': 32 MB region '25': 64 MB region '26': 128 MB region '27': 256 MB region '28': 512 MB region '39': 1 GB region '30': 2 GB region '31': 4 GB region
31	ENABLED	RW	RW	0	Region enable: '0': Disabled. A disabled region will never result in a match on the bus transfer address. '1': Enabled. Note: a disabled address region performs logic gating to reduce dynamic power consumption.

24 SCB

24.1 SCB 0

Description	Serial Communications Block (SPI/UART/I2C)
Base Address	0x40600000
Size	0x10000
Slave Num	MMIO6 - 0

Register Name	Address	Permission	Description
SCB0_CTRL	0x40600000	FULL	Generic control
SCB0_STATUS	0x40600004	FULL	Generic status
SCB0_CMD_RESP_CTRL	0x40600008	FULL	Command/response control
SCB0_CMD_RESP_STATUS	0x4060000C	FULL	Command/response status
SCB0_SPI_CTRL	0x40600020	FULL	SPI control
SCB0_SPI_STATUS	0x40600024	FULL	SPI status
SCB0_SPI_TX_CTRL	0x40600028	FULL	SPI transmitter control
SCB0_SPI_RX_CTRL	0x4060002C	FULL	SPI receiver control
SCB0_UART_CTRL	0x40600040	FULL	UART control
SCB0_UART_TX_CTRL	0x40600044	FULL	UART transmitter control
SCB0_UART_RX_CTRL	0x40600048	FULL	UART receiver control
SCB0_UART_RX_STATUS	0x4060004C	FULL	UART receiver status
SCB0_UART_FLOW_CTRL	0x40600050	FULL	UART flow control
SCB0_I2C_CTRL	0x40600060	FULL	I2C control
SCB0_I2C_STATUS	0x40600064	FULL	I2C status
SCB0_I2C_M_CMD	0x40600068	FULL	I2C master command
SCB0_I2C_S_CMD	0x4060006C	FULL	I2C slave command
SCB0_I2C_CFG	0x40600070	FULL	I2C configuration
SCB0_TX_CTRL	0x40600200	FULL	Transmitter control
SCB0_TX_FIFO_CTRL	0x40600204	FULL	Transmitter FIFO control
SCB0_TX_FIFO_STATUS	0x40600208	FULL	Transmitter FIFO status
SCB0_TX_FIFO_WR	0x40600240	FULL	Transmitter FIFO write
SCB0_RX_CTRL	0x40600300	FULL	Receiver control
SCB0_RX_FIFO_CTRL	0x40600304	FULL	Receiver FIFO control
SCB0_RX_FIFO_STATUS	0x40600308	FULL	Receiver FIFO status
SCB0_RX_MATCH	0x40600310	FULL	Slave address and mask
SCB0_RX_FIFO_RD	0x40600340	FULL	Receiver FIFO read
SCB0_RX_FIFO_RD_SILENT	0x40600344	FULL	Receiver FIFO read silent
SCB0_EZ_DATA0	0x40600400	FULL	Memory buffer
SCB0_EZ_DATA1	0x40600404	FULL	Memory buffer
SCB0_EZ_DATA2	0x40600408	FULL	Memory buffer
SCB0_EZ_DATA3	0x4060040C	FULL	Memory buffer
SCB0_EZ_DATA4	0x40600410	FULL	Memory buffer
SCB0_EZ_DATA5	0x40600414	FULL	Memory buffer
SCB0_EZ_DATA6	0x40600418	FULL	Memory buffer
SCB0_EZ_DATA7	0x4060041C	FULL	Memory buffer
SCB0_EZ_DATA8	0x40600420	FULL	Memory buffer
SCB0_EZ_DATA9	0x40600424	FULL	Memory buffer
SCB0_EZ_DATA10	0x40600428	FULL	Memory buffer
SCB0_EZ_DATA11	0x4060042C	FULL	Memory buffer
SCB0_EZ_DATA12	0x40600430	FULL	Memory buffer
SCB0_EZ_DATA13	0x40600434	FULL	Memory buffer
SCB0_EZ_DATA14	0x40600438	FULL	Memory buffer
SCB0_EZ_DATA15	0x4060043C	FULL	Memory buffer
SCB0_EZ_DATA16	0x40600440	FULL	Memory buffer
SCB0_EZ_DATA17	0x40600444	FULL	Memory buffer
SCB0_EZ_DATA18	0x40600448	FULL	Memory buffer
SCB0_EZ_DATA19	0x4060044C	FULL	Memory buffer
SCB0_EZ_DATA20	0x40600450	FULL	Memory buffer
SCB0_EZ_DATA21	0x40600454	FULL	Memory buffer
SCB0_EZ_DATA22	0x40600458	FULL	Memory buffer
SCB0_EZ_DATA23	0x4060045C	FULL	Memory buffer
SCB0_EZ_DATA24	0x40600460	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB0_EZ_DATA25	0x40600464	FULL	Memory buffer
SCB0_EZ_DATA26	0x40600468	FULL	Memory buffer
SCB0_EZ_DATA27	0x4060046C	FULL	Memory buffer
SCB0_EZ_DATA28	0x40600470	FULL	Memory buffer
SCB0_EZ_DATA29	0x40600474	FULL	Memory buffer
SCB0_EZ_DATA30	0x40600478	FULL	Memory buffer
SCB0_EZ_DATA31	0x4060047C	FULL	Memory buffer
SCB0_EZ_DATA32	0x40600480	FULL	Memory buffer
SCB0_EZ_DATA33	0x40600484	FULL	Memory buffer
SCB0_EZ_DATA34	0x40600488	FULL	Memory buffer
SCB0_EZ_DATA35	0x4060048C	FULL	Memory buffer
SCB0_EZ_DATA36	0x40600490	FULL	Memory buffer
SCB0_EZ_DATA37	0x40600494	FULL	Memory buffer
SCB0_EZ_DATA38	0x40600498	FULL	Memory buffer
SCB0_EZ_DATA39	0x4060049C	FULL	Memory buffer
SCB0_EZ_DATA40	0x406004A0	FULL	Memory buffer
SCB0_EZ_DATA41	0x406004A4	FULL	Memory buffer
SCB0_EZ_DATA42	0x406004A8	FULL	Memory buffer
SCB0_EZ_DATA43	0x406004AC	FULL	Memory buffer
SCB0_EZ_DATA44	0x406004B0	FULL	Memory buffer
SCB0_EZ_DATA45	0x406004B4	FULL	Memory buffer
SCB0_EZ_DATA46	0x406004B8	FULL	Memory buffer
SCB0_EZ_DATA47	0x406004BC	FULL	Memory buffer
SCB0_EZ_DATA48	0x406004C0	FULL	Memory buffer
SCB0_EZ_DATA49	0x406004C4	FULL	Memory buffer
SCB0_EZ_DATA50	0x406004C8	FULL	Memory buffer
SCB0_EZ_DATA51	0x406004CC	FULL	Memory buffer
SCB0_EZ_DATA52	0x406004D0	FULL	Memory buffer
SCB0_EZ_DATA53	0x406004D4	FULL	Memory buffer
SCB0_EZ_DATA54	0x406004D8	FULL	Memory buffer
SCB0_EZ_DATA55	0x406004DC	FULL	Memory buffer
SCB0_EZ_DATA56	0x406004E0	FULL	Memory buffer
SCB0_EZ_DATA57	0x406004E4	FULL	Memory buffer
SCB0_EZ_DATA58	0x406004E8	FULL	Memory buffer
SCB0_EZ_DATA59	0x406004EC	FULL	Memory buffer
SCB0_EZ_DATA60	0x406004F0	FULL	Memory buffer
SCB0_EZ_DATA61	0x406004F4	FULL	Memory buffer
SCB0_EZ_DATA62	0x406004F8	FULL	Memory buffer
SCB0_EZ_DATA63	0x406004FC	FULL	Memory buffer
SCB0_EZ_DATA64	0x40600500	FULL	Memory buffer
SCB0_EZ_DATA65	0x40600504	FULL	Memory buffer
SCB0_EZ_DATA66	0x40600508	FULL	Memory buffer
SCB0_EZ_DATA67	0x4060050C	FULL	Memory buffer
SCB0_EZ_DATA68	0x40600510	FULL	Memory buffer
SCB0_EZ_DATA69	0x40600514	FULL	Memory buffer
SCB0_EZ_DATA70	0x40600518	FULL	Memory buffer
SCB0_EZ_DATA71	0x4060051C	FULL	Memory buffer
SCB0_EZ_DATA72	0x40600520	FULL	Memory buffer
SCB0_EZ_DATA73	0x40600524	FULL	Memory buffer
SCB0_EZ_DATA74	0x40600528	FULL	Memory buffer
SCB0_EZ_DATA75	0x4060052C	FULL	Memory buffer
SCB0_EZ_DATA76	0x40600530	FULL	Memory buffer
SCB0_EZ_DATA77	0x40600534	FULL	Memory buffer
SCB0_EZ_DATA78	0x40600538	FULL	Memory buffer
SCB0_EZ_DATA79	0x4060053C	FULL	Memory buffer
SCB0_EZ_DATA80	0x40600540	FULL	Memory buffer
SCB0_EZ_DATA81	0x40600544	FULL	Memory buffer
SCB0_EZ_DATA82	0x40600548	FULL	Memory buffer
SCB0_EZ_DATA83	0x4060054C	FULL	Memory buffer
SCB0_EZ_DATA84	0x40600550	FULL	Memory buffer
SCB0_EZ_DATA85	0x40600554	FULL	Memory buffer
SCB0_EZ_DATA86	0x40600558	FULL	Memory buffer
SCB0_EZ_DATA87	0x4060055C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB0_EZ_DATA88	0x40600560	FULL	Memory buffer
SCB0_EZ_DATA89	0x40600564	FULL	Memory buffer
SCB0_EZ_DATA90	0x40600568	FULL	Memory buffer
SCB0_EZ_DATA91	0x4060056C	FULL	Memory buffer
SCB0_EZ_DATA92	0x40600570	FULL	Memory buffer
SCB0_EZ_DATA93	0x40600574	FULL	Memory buffer
SCB0_EZ_DATA94	0x40600578	FULL	Memory buffer
SCB0_EZ_DATA95	0x4060057C	FULL	Memory buffer
SCB0_EZ_DATA96	0x40600580	FULL	Memory buffer
SCB0_EZ_DATA97	0x40600584	FULL	Memory buffer
SCB0_EZ_DATA98	0x40600588	FULL	Memory buffer
SCB0_EZ_DATA99	0x4060058C	FULL	Memory buffer
SCB0_EZ_DATA100	0x40600590	FULL	Memory buffer
SCB0_EZ_DATA101	0x40600594	FULL	Memory buffer
SCB0_EZ_DATA102	0x40600598	FULL	Memory buffer
SCB0_EZ_DATA103	0x4060059C	FULL	Memory buffer
SCB0_EZ_DATA104	0x406005A0	FULL	Memory buffer
SCB0_EZ_DATA105	0x406005A4	FULL	Memory buffer
SCB0_EZ_DATA106	0x406005A8	FULL	Memory buffer
SCB0_EZ_DATA107	0x406005AC	FULL	Memory buffer
SCB0_EZ_DATA108	0x406005B0	FULL	Memory buffer
SCB0_EZ_DATA109	0x406005B4	FULL	Memory buffer
SCB0_EZ_DATA110	0x406005B8	FULL	Memory buffer
SCB0_EZ_DATA111	0x406005BC	FULL	Memory buffer
SCB0_EZ_DATA112	0x406005C0	FULL	Memory buffer
SCB0_EZ_DATA113	0x406005C4	FULL	Memory buffer
SCB0_EZ_DATA114	0x406005C8	FULL	Memory buffer
SCB0_EZ_DATA115	0x406005CC	FULL	Memory buffer
SCB0_EZ_DATA116	0x406005D0	FULL	Memory buffer
SCB0_EZ_DATA117	0x406005D4	FULL	Memory buffer
SCB0_EZ_DATA118	0x406005D8	FULL	Memory buffer
SCB0_EZ_DATA119	0x406005DC	FULL	Memory buffer
SCB0_EZ_DATA120	0x406005E0	FULL	Memory buffer
SCB0_EZ_DATA121	0x406005E4	FULL	Memory buffer
SCB0_EZ_DATA122	0x406005E8	FULL	Memory buffer
SCB0_EZ_DATA123	0x406005EC	FULL	Memory buffer
SCB0_EZ_DATA124	0x406005F0	FULL	Memory buffer
SCB0_EZ_DATA125	0x406005F4	FULL	Memory buffer
SCB0_EZ_DATA126	0x406005F8	FULL	Memory buffer
SCB0_EZ_DATA127	0x406005FC	FULL	Memory buffer
SCB0_EZ_DATA128	0x40600600	FULL	Memory buffer
SCB0_EZ_DATA129	0x40600604	FULL	Memory buffer
SCB0_EZ_DATA130	0x40600608	FULL	Memory buffer
SCB0_EZ_DATA131	0x4060060C	FULL	Memory buffer
SCB0_EZ_DATA132	0x40600610	FULL	Memory buffer
SCB0_EZ_DATA133	0x40600614	FULL	Memory buffer
SCB0_EZ_DATA134	0x40600618	FULL	Memory buffer
SCB0_EZ_DATA135	0x4060061C	FULL	Memory buffer
SCB0_EZ_DATA136	0x40600620	FULL	Memory buffer
SCB0_EZ_DATA137	0x40600624	FULL	Memory buffer
SCB0_EZ_DATA138	0x40600628	FULL	Memory buffer
SCB0_EZ_DATA139	0x4060062C	FULL	Memory buffer
SCB0_EZ_DATA140	0x40600630	FULL	Memory buffer
SCB0_EZ_DATA141	0x40600634	FULL	Memory buffer
SCB0_EZ_DATA142	0x40600638	FULL	Memory buffer
SCB0_EZ_DATA143	0x4060063C	FULL	Memory buffer
SCB0_EZ_DATA144	0x40600640	FULL	Memory buffer
SCB0_EZ_DATA145	0x40600644	FULL	Memory buffer
SCB0_EZ_DATA146	0x40600648	FULL	Memory buffer
SCB0_EZ_DATA147	0x4060064C	FULL	Memory buffer
SCB0_EZ_DATA148	0x40600650	FULL	Memory buffer
SCB0_EZ_DATA149	0x40600654	FULL	Memory buffer
SCB0_EZ_DATA150	0x40600658	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB0_EZ_DATA151	0x4060065C	FULL	Memory buffer
SCB0_EZ_DATA152	0x40600660	FULL	Memory buffer
SCB0_EZ_DATA153	0x40600664	FULL	Memory buffer
SCB0_EZ_DATA154	0x40600668	FULL	Memory buffer
SCB0_EZ_DATA155	0x4060066C	FULL	Memory buffer
SCB0_EZ_DATA156	0x40600670	FULL	Memory buffer
SCB0_EZ_DATA157	0x40600674	FULL	Memory buffer
SCB0_EZ_DATA158	0x40600678	FULL	Memory buffer
SCB0_EZ_DATA159	0x4060067C	FULL	Memory buffer
SCB0_EZ_DATA160	0x40600680	FULL	Memory buffer
SCB0_EZ_DATA161	0x40600684	FULL	Memory buffer
SCB0_EZ_DATA162	0x40600688	FULL	Memory buffer
SCB0_EZ_DATA163	0x4060068C	FULL	Memory buffer
SCB0_EZ_DATA164	0x40600690	FULL	Memory buffer
SCB0_EZ_DATA165	0x40600694	FULL	Memory buffer
SCB0_EZ_DATA166	0x40600698	FULL	Memory buffer
SCB0_EZ_DATA167	0x4060069C	FULL	Memory buffer
SCB0_EZ_DATA168	0x406006A0	FULL	Memory buffer
SCB0_EZ_DATA169	0x406006A4	FULL	Memory buffer
SCB0_EZ_DATA170	0x406006A8	FULL	Memory buffer
SCB0_EZ_DATA171	0x406006AC	FULL	Memory buffer
SCB0_EZ_DATA172	0x406006B0	FULL	Memory buffer
SCB0_EZ_DATA173	0x406006B4	FULL	Memory buffer
SCB0_EZ_DATA174	0x406006B8	FULL	Memory buffer
SCB0_EZ_DATA175	0x406006BC	FULL	Memory buffer
SCB0_EZ_DATA176	0x406006C0	FULL	Memory buffer
SCB0_EZ_DATA177	0x406006C4	FULL	Memory buffer
SCB0_EZ_DATA178	0x406006C8	FULL	Memory buffer
SCB0_EZ_DATA179	0x406006CC	FULL	Memory buffer
SCB0_EZ_DATA180	0x406006D0	FULL	Memory buffer
SCB0_EZ_DATA181	0x406006D4	FULL	Memory buffer
SCB0_EZ_DATA182	0x406006D8	FULL	Memory buffer
SCB0_EZ_DATA183	0x406006DC	FULL	Memory buffer
SCB0_EZ_DATA184	0x406006E0	FULL	Memory buffer
SCB0_EZ_DATA185	0x406006E4	FULL	Memory buffer
SCB0_EZ_DATA186	0x406006E8	FULL	Memory buffer
SCB0_EZ_DATA187	0x406006EC	FULL	Memory buffer
SCB0_EZ_DATA188	0x406006F0	FULL	Memory buffer
SCB0_EZ_DATA189	0x406006F4	FULL	Memory buffer
SCB0_EZ_DATA190	0x406006F8	FULL	Memory buffer
SCB0_EZ_DATA191	0x406006FC	FULL	Memory buffer
SCB0_EZ_DATA192	0x40600700	FULL	Memory buffer
SCB0_EZ_DATA193	0x40600704	FULL	Memory buffer
SCB0_EZ_DATA194	0x40600708	FULL	Memory buffer
SCB0_EZ_DATA195	0x4060070C	FULL	Memory buffer
SCB0_EZ_DATA196	0x40600710	FULL	Memory buffer
SCB0_EZ_DATA197	0x40600714	FULL	Memory buffer
SCB0_EZ_DATA198	0x40600718	FULL	Memory buffer
SCB0_EZ_DATA199	0x4060071C	FULL	Memory buffer
SCB0_EZ_DATA200	0x40600720	FULL	Memory buffer
SCB0_EZ_DATA201	0x40600724	FULL	Memory buffer
SCB0_EZ_DATA202	0x40600728	FULL	Memory buffer
SCB0_EZ_DATA203	0x4060072C	FULL	Memory buffer
SCB0_EZ_DATA204	0x40600730	FULL	Memory buffer
SCB0_EZ_DATA205	0x40600734	FULL	Memory buffer
SCB0_EZ_DATA206	0x40600738	FULL	Memory buffer
SCB0_EZ_DATA207	0x4060073C	FULL	Memory buffer
SCB0_EZ_DATA208	0x40600740	FULL	Memory buffer
SCB0_EZ_DATA209	0x40600744	FULL	Memory buffer
SCB0_EZ_DATA210	0x40600748	FULL	Memory buffer
SCB0_EZ_DATA211	0x4060074C	FULL	Memory buffer
SCB0_EZ_DATA212	0x40600750	FULL	Memory buffer
SCB0_EZ_DATA213	0x40600754	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB0_EZ_DATA214	0x40600758	FULL	Memory buffer
SCB0_EZ_DATA215	0x4060075C	FULL	Memory buffer
SCB0_EZ_DATA216	0x40600760	FULL	Memory buffer
SCB0_EZ_DATA217	0x40600764	FULL	Memory buffer
SCB0_EZ_DATA218	0x40600768	FULL	Memory buffer
SCB0_EZ_DATA219	0x4060076C	FULL	Memory buffer
SCB0_EZ_DATA220	0x40600770	FULL	Memory buffer
SCB0_EZ_DATA221	0x40600774	FULL	Memory buffer
SCB0_EZ_DATA222	0x40600778	FULL	Memory buffer
SCB0_EZ_DATA223	0x4060077C	FULL	Memory buffer
SCB0_EZ_DATA224	0x40600780	FULL	Memory buffer
SCB0_EZ_DATA225	0x40600784	FULL	Memory buffer
SCB0_EZ_DATA226	0x40600788	FULL	Memory buffer
SCB0_EZ_DATA227	0x4060078C	FULL	Memory buffer
SCB0_EZ_DATA228	0x40600790	FULL	Memory buffer
SCB0_EZ_DATA229	0x40600794	FULL	Memory buffer
SCB0_EZ_DATA230	0x40600798	FULL	Memory buffer
SCB0_EZ_DATA231	0x4060079C	FULL	Memory buffer
SCB0_EZ_DATA232	0x406007A0	FULL	Memory buffer
SCB0_EZ_DATA233	0x406007A4	FULL	Memory buffer
SCB0_EZ_DATA234	0x406007A8	FULL	Memory buffer
SCB0_EZ_DATA235	0x406007AC	FULL	Memory buffer
SCB0_EZ_DATA236	0x406007B0	FULL	Memory buffer
SCB0_EZ_DATA237	0x406007B4	FULL	Memory buffer
SCB0_EZ_DATA238	0x406007B8	FULL	Memory buffer
SCB0_EZ_DATA239	0x406007BC	FULL	Memory buffer
SCB0_EZ_DATA240	0x406007C0	FULL	Memory buffer
SCB0_EZ_DATA241	0x406007C4	FULL	Memory buffer
SCB0_EZ_DATA242	0x406007C8	FULL	Memory buffer
SCB0_EZ_DATA243	0x406007CC	FULL	Memory buffer
SCB0_EZ_DATA244	0x406007D0	FULL	Memory buffer
SCB0_EZ_DATA245	0x406007D4	FULL	Memory buffer
SCB0_EZ_DATA246	0x406007D8	FULL	Memory buffer
SCB0_EZ_DATA247	0x406007DC	FULL	Memory buffer
SCB0_EZ_DATA248	0x406007E0	FULL	Memory buffer
SCB0_EZ_DATA249	0x406007E4	FULL	Memory buffer
SCB0_EZ_DATA250	0x406007E8	FULL	Memory buffer
SCB0_EZ_DATA251	0x406007EC	FULL	Memory buffer
SCB0_EZ_DATA252	0x406007F0	FULL	Memory buffer
SCB0_EZ_DATA253	0x406007F4	FULL	Memory buffer
SCB0_EZ_DATA254	0x406007F8	FULL	Memory buffer
SCB0_EZ_DATA255	0x406007FC	FULL	Memory buffer
SCB0_INTR_CAUSE	0x40600E00	FULL	Active clocked interrupt signal
SCB0_INTR_I2C_EC	0x40600E80	FULL	Externally clocked I2C interrupt request
SCB0_INTR_I2C_EC_MASK	0x40600E88	FULL	Externally clocked I2C interrupt mask
SCB0_INTR_I2C_EC_MASKED	0x40600E8C	FULL	Externally clocked I2C interrupt masked
SCB0_INTR_SPI_EC	0x40600EC0	FULL	Externally clocked SPI interrupt request
SCB0_INTR_SPI_EC_MASK	0x40600EC8	FULL	Externally clocked SPI interrupt mask
SCB0_INTR_SPI_EC_MASKED	0x40600ECC	FULL	Externally clocked SPI interrupt masked
SCB0_INTR_M	0x40600F00	FULL	Master interrupt request
SCB0_INTR_M_SET	0x40600F04	FULL	Master interrupt set request
SCB0_INTR_M_MASK	0x40600F08	FULL	Master interrupt mask
SCB0_INTR_M_MASKED	0x40600F0C	FULL	Master interrupt masked request
SCB0_INTR_S	0x40600F40	FULL	Slave interrupt request
SCB0_INTR_S_SET	0x40600F44	FULL	Slave interrupt set request
SCB0_INTR_S_MASK	0x40600F48	FULL	Slave interrupt mask
SCB0_INTR_S_MASKED	0x40600F4C	FULL	Slave interrupt masked request
SCB0_INTR_TX	0x40600F80	FULL	Transmitter interrupt request
SCB0_INTR_TX_SET	0x40600F84	FULL	Transmitter interrupt set request
SCB0_INTR_TX_MASK	0x40600F88	FULL	Transmitter interrupt mask
SCB0_INTR_TX_MASKED	0x40600F8C	FULL	Transmitter interrupt masked request
SCB0_INTR_RX	0x40600FC0	FULL	Receiver interrupt request
SCB0_INTR_RX_SET	0x40600FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB0_INTR_RX_MASK	0x40600FC8	FULL	Receiver interrupt mask
SCB0_INTR_RX_MASKED	0x40600FCC	FULL	Receiver interrupt masked request

24.2 SCB 1

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40610000

Size 0x10000

Slave Num MMIO6 - 1

Register Name	Address	Permission	Description
SCB1_CTRL	0x40610000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB1_STATUS	0x40610004	FULL	Generic status
SCB1_SPI_CTRL	0x40610020	FULL	SPI control
SCB1_SPI_STATUS	0x40610024	FULL	SPI status
SCB1_SPI_TX_CTRL	0x40610028	FULL	SPI transmitter control
SCB1_SPI_RX_CTRL	0x4061002C	FULL	SPI receiver control
SCB1_UART_CTRL	0x40610040	FULL	UART control
SCB1_UART_TX_CTRL	0x40610044	FULL	UART transmitter control
SCB1_UART_RX_CTRL	0x40610048	FULL	UART receiver control
SCB1_UART_RX_STATUS	0x4061004C	FULL	UART receiver status
SCB1_UART_FLOW_CTRL	0x40610050	FULL	UART flow control
SCB1_I2C_CTRL	0x40610060	FULL	I2C control
SCB1_I2C_STATUS	0x40610064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB1_I2C_M_CMD	0x40610068	FULL	I2C master command
SCB1_I2C_S_CMD	0x4061006C	FULL	I2C slave command
SCB1_I2C_CFG	0x40610070	FULL	I2C configuration
SCB1_TX_CTRL	0x40610200	FULL	Transmitter control
SCB1_TX_FIFO_CTRL	0x40610204	FULL	Transmitter FIFO control
SCB1_TX_FIFO_STATUS	0x40610208	FULL	Transmitter FIFO status
SCB1_TX_FIFO_WR	0x40610240	FULL	Transmitter FIFO write
SCB1_RX_CTRL	0x40610300	FULL	Receiver control
SCB1_RX_FIFO_CTRL	0x40610304	FULL	Receiver FIFO control
SCB1_RX_FIFO_STATUS	0x40610308	FULL	Receiver FIFO status
SCB1_RX_MATCH	0x40610310	FULL	Slave address and mask
SCB1_RX_FIFO_RD	0x40610340	FULL	Receiver FIFO read
SCB1_RX_FIFO_RD_SILENT	0x40610344	FULL	Receiver FIFO read silent
SCB1_EZ_DATA0	0x40610400	FULL	Memory buffer
SCB1_EZ_DATA1	0x40610404	FULL	Memory buffer
SCB1_EZ_DATA2	0x40610408	FULL	Memory buffer
SCB1_EZ_DATA3	0x4061040C	FULL	Memory buffer
SCB1_EZ_DATA4	0x40610410	FULL	Memory buffer
SCB1_EZ_DATA5	0x40610414	FULL	Memory buffer
SCB1_EZ_DATA6	0x40610418	FULL	Memory buffer
SCB1_EZ_DATA7	0x4061041C	FULL	Memory buffer
SCB1_EZ_DATA8	0x40610420	FULL	Memory buffer
SCB1_EZ_DATA9	0x40610424	FULL	Memory buffer
SCB1_EZ_DATA10	0x40610428	FULL	Memory buffer
SCB1_EZ_DATA11	0x4061042C	FULL	Memory buffer
SCB1_EZ_DATA12	0x40610430	FULL	Memory buffer
SCB1_EZ_DATA13	0x40610434	FULL	Memory buffer
SCB1_EZ_DATA14	0x40610438	FULL	Memory buffer
SCB1_EZ_DATA15	0x4061043C	FULL	Memory buffer
SCB1_EZ_DATA16	0x40610440	FULL	Memory buffer
SCB1_EZ_DATA17	0x40610444	FULL	Memory buffer
SCB1_EZ_DATA18	0x40610448	FULL	Memory buffer
SCB1_EZ_DATA19	0x4061044C	FULL	Memory buffer
SCB1_EZ_DATA20	0x40610450	FULL	Memory buffer
SCB1_EZ_DATA21	0x40610454	FULL	Memory buffer
SCB1_EZ_DATA22	0x40610458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB1_EZ_DATA23	0x4061045C	FULL	Memory buffer
SCB1_EZ_DATA24	0x40610460	FULL	Memory buffer
SCB1_EZ_DATA25	0x40610464	FULL	Memory buffer
SCB1_EZ_DATA26	0x40610468	FULL	Memory buffer
SCB1_EZ_DATA27	0x4061046C	FULL	Memory buffer
SCB1_EZ_DATA28	0x40610470	FULL	Memory buffer
SCB1_EZ_DATA29	0x40610474	FULL	Memory buffer
SCB1_EZ_DATA30	0x40610478	FULL	Memory buffer
SCB1_EZ_DATA31	0x4061047C	FULL	Memory buffer
SCB1_EZ_DATA32	0x40610480	FULL	Memory buffer
SCB1_EZ_DATA33	0x40610484	FULL	Memory buffer
SCB1_EZ_DATA34	0x40610488	FULL	Memory buffer
SCB1_EZ_DATA35	0x4061048C	FULL	Memory buffer
SCB1_EZ_DATA36	0x40610490	FULL	Memory buffer
SCB1_EZ_DATA37	0x40610494	FULL	Memory buffer
SCB1_EZ_DATA38	0x40610498	FULL	Memory buffer
SCB1_EZ_DATA39	0x4061049C	FULL	Memory buffer
SCB1_EZ_DATA40	0x406104A0	FULL	Memory buffer
SCB1_EZ_DATA41	0x406104A4	FULL	Memory buffer
SCB1_EZ_DATA42	0x406104A8	FULL	Memory buffer
SCB1_EZ_DATA43	0x406104AC	FULL	Memory buffer
SCB1_EZ_DATA44	0x406104B0	FULL	Memory buffer
SCB1_EZ_DATA45	0x406104B4	FULL	Memory buffer
SCB1_EZ_DATA46	0x406104B8	FULL	Memory buffer
SCB1_EZ_DATA47	0x406104BC	FULL	Memory buffer
SCB1_EZ_DATA48	0x406104C0	FULL	Memory buffer
SCB1_EZ_DATA49	0x406104C4	FULL	Memory buffer
SCB1_EZ_DATA50	0x406104C8	FULL	Memory buffer
SCB1_EZ_DATA51	0x406104CC	FULL	Memory buffer
SCB1_EZ_DATA52	0x406104D0	FULL	Memory buffer
SCB1_EZ_DATA53	0x406104D4	FULL	Memory buffer
SCB1_EZ_DATA54	0x406104D8	FULL	Memory buffer
SCB1_EZ_DATA55	0x406104DC	FULL	Memory buffer
SCB1_EZ_DATA56	0x406104E0	FULL	Memory buffer
SCB1_EZ_DATA57	0x406104E4	FULL	Memory buffer
SCB1_EZ_DATA58	0x406104E8	FULL	Memory buffer
SCB1_EZ_DATA59	0x406104EC	FULL	Memory buffer
SCB1_EZ_DATA60	0x406104F0	FULL	Memory buffer
SCB1_EZ_DATA61	0x406104F4	FULL	Memory buffer
SCB1_EZ_DATA62	0x406104F8	FULL	Memory buffer
SCB1_EZ_DATA63	0x406104FC	FULL	Memory buffer
SCB1_EZ_DATA64	0x40610500	FULL	Memory buffer
SCB1_EZ_DATA65	0x40610504	FULL	Memory buffer
SCB1_EZ_DATA66	0x40610508	FULL	Memory buffer
SCB1_EZ_DATA67	0x4061050C	FULL	Memory buffer
SCB1_EZ_DATA68	0x40610510	FULL	Memory buffer
SCB1_EZ_DATA69	0x40610514	FULL	Memory buffer
SCB1_EZ_DATA70	0x40610518	FULL	Memory buffer
SCB1_EZ_DATA71	0x4061051C	FULL	Memory buffer
SCB1_EZ_DATA72	0x40610520	FULL	Memory buffer
SCB1_EZ_DATA73	0x40610524	FULL	Memory buffer
SCB1_EZ_DATA74	0x40610528	FULL	Memory buffer
SCB1_EZ_DATA75	0x4061052C	FULL	Memory buffer
SCB1_EZ_DATA76	0x40610530	FULL	Memory buffer
SCB1_EZ_DATA77	0x40610534	FULL	Memory buffer
SCB1_EZ_DATA78	0x40610538	FULL	Memory buffer
SCB1_EZ_DATA79	0x4061053C	FULL	Memory buffer
SCB1_EZ_DATA80	0x40610540	FULL	Memory buffer
SCB1_EZ_DATA81	0x40610544	FULL	Memory buffer
SCB1_EZ_DATA82	0x40610548	FULL	Memory buffer
SCB1_EZ_DATA83	0x4061054C	FULL	Memory buffer
SCB1_EZ_DATA84	0x40610550	FULL	Memory buffer
SCB1_EZ_DATA85	0x40610554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB1_EZ_DATA86	0x40610558	FULL	Memory buffer
SCB1_EZ_DATA87	0x4061055C	FULL	Memory buffer
SCB1_EZ_DATA88	0x40610560	FULL	Memory buffer
SCB1_EZ_DATA89	0x40610564	FULL	Memory buffer
SCB1_EZ_DATA90	0x40610568	FULL	Memory buffer
SCB1_EZ_DATA91	0x4061056C	FULL	Memory buffer
SCB1_EZ_DATA92	0x40610570	FULL	Memory buffer
SCB1_EZ_DATA93	0x40610574	FULL	Memory buffer
SCB1_EZ_DATA94	0x40610578	FULL	Memory buffer
SCB1_EZ_DATA95	0x4061057C	FULL	Memory buffer
SCB1_EZ_DATA96	0x40610580	FULL	Memory buffer
SCB1_EZ_DATA97	0x40610584	FULL	Memory buffer
SCB1_EZ_DATA98	0x40610588	FULL	Memory buffer
SCB1_EZ_DATA99	0x4061058C	FULL	Memory buffer
SCB1_EZ_DATA100	0x40610590	FULL	Memory buffer
SCB1_EZ_DATA101	0x40610594	FULL	Memory buffer
SCB1_EZ_DATA102	0x40610598	FULL	Memory buffer
SCB1_EZ_DATA103	0x4061059C	FULL	Memory buffer
SCB1_EZ_DATA104	0x406105A0	FULL	Memory buffer
SCB1_EZ_DATA105	0x406105A4	FULL	Memory buffer
SCB1_EZ_DATA106	0x406105A8	FULL	Memory buffer
SCB1_EZ_DATA107	0x406105AC	FULL	Memory buffer
SCB1_EZ_DATA108	0x406105B0	FULL	Memory buffer
SCB1_EZ_DATA109	0x406105B4	FULL	Memory buffer
SCB1_EZ_DATA110	0x406105B8	FULL	Memory buffer
SCB1_EZ_DATA111	0x406105BC	FULL	Memory buffer
SCB1_EZ_DATA112	0x406105C0	FULL	Memory buffer
SCB1_EZ_DATA113	0x406105C4	FULL	Memory buffer
SCB1_EZ_DATA114	0x406105C8	FULL	Memory buffer
SCB1_EZ_DATA115	0x406105CC	FULL	Memory buffer
SCB1_EZ_DATA116	0x406105D0	FULL	Memory buffer
SCB1_EZ_DATA117	0x406105D4	FULL	Memory buffer
SCB1_EZ_DATA118	0x406105D8	FULL	Memory buffer
SCB1_EZ_DATA119	0x406105DC	FULL	Memory buffer
SCB1_EZ_DATA120	0x406105E0	FULL	Memory buffer
SCB1_EZ_DATA121	0x406105E4	FULL	Memory buffer
SCB1_EZ_DATA122	0x406105E8	FULL	Memory buffer
SCB1_EZ_DATA123	0x406105EC	FULL	Memory buffer
SCB1_EZ_DATA124	0x406105F0	FULL	Memory buffer
SCB1_EZ_DATA125	0x406105F4	FULL	Memory buffer
SCB1_EZ_DATA126	0x406105F8	FULL	Memory buffer
SCB1_EZ_DATA127	0x406105FC	FULL	Memory buffer
SCB1_EZ_DATA128	0x40610600	FULL	Memory buffer
SCB1_EZ_DATA129	0x40610604	FULL	Memory buffer
SCB1_EZ_DATA130	0x40610608	FULL	Memory buffer
SCB1_EZ_DATA131	0x4061060C	FULL	Memory buffer
SCB1_EZ_DATA132	0x40610610	FULL	Memory buffer
SCB1_EZ_DATA133	0x40610614	FULL	Memory buffer
SCB1_EZ_DATA134	0x40610618	FULL	Memory buffer
SCB1_EZ_DATA135	0x4061061C	FULL	Memory buffer
SCB1_EZ_DATA136	0x40610620	FULL	Memory buffer
SCB1_EZ_DATA137	0x40610624	FULL	Memory buffer
SCB1_EZ_DATA138	0x40610628	FULL	Memory buffer
SCB1_EZ_DATA139	0x4061062C	FULL	Memory buffer
SCB1_EZ_DATA140	0x40610630	FULL	Memory buffer
SCB1_EZ_DATA141	0x40610634	FULL	Memory buffer
SCB1_EZ_DATA142	0x40610638	FULL	Memory buffer
SCB1_EZ_DATA143	0x4061063C	FULL	Memory buffer
SCB1_EZ_DATA144	0x40610640	FULL	Memory buffer
SCB1_EZ_DATA145	0x40610644	FULL	Memory buffer
SCB1_EZ_DATA146	0x40610648	FULL	Memory buffer
SCB1_EZ_DATA147	0x4061064C	FULL	Memory buffer
SCB1_EZ_DATA148	0x40610650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB1_EZ_DATA149	0x40610654	FULL	Memory buffer
SCB1_EZ_DATA150	0x40610658	FULL	Memory buffer
SCB1_EZ_DATA151	0x4061065C	FULL	Memory buffer
SCB1_EZ_DATA152	0x40610660	FULL	Memory buffer
SCB1_EZ_DATA153	0x40610664	FULL	Memory buffer
SCB1_EZ_DATA154	0x40610668	FULL	Memory buffer
SCB1_EZ_DATA155	0x4061066C	FULL	Memory buffer
SCB1_EZ_DATA156	0x40610670	FULL	Memory buffer
SCB1_EZ_DATA157	0x40610674	FULL	Memory buffer
SCB1_EZ_DATA158	0x40610678	FULL	Memory buffer
SCB1_EZ_DATA159	0x4061067C	FULL	Memory buffer
SCB1_EZ_DATA160	0x40610680	FULL	Memory buffer
SCB1_EZ_DATA161	0x40610684	FULL	Memory buffer
SCB1_EZ_DATA162	0x40610688	FULL	Memory buffer
SCB1_EZ_DATA163	0x4061068C	FULL	Memory buffer
SCB1_EZ_DATA164	0x40610690	FULL	Memory buffer
SCB1_EZ_DATA165	0x40610694	FULL	Memory buffer
SCB1_EZ_DATA166	0x40610698	FULL	Memory buffer
SCB1_EZ_DATA167	0x4061069C	FULL	Memory buffer
SCB1_EZ_DATA168	0x406106A0	FULL	Memory buffer
SCB1_EZ_DATA169	0x406106A4	FULL	Memory buffer
SCB1_EZ_DATA170	0x406106A8	FULL	Memory buffer
SCB1_EZ_DATA171	0x406106AC	FULL	Memory buffer
SCB1_EZ_DATA172	0x406106B0	FULL	Memory buffer
SCB1_EZ_DATA173	0x406106B4	FULL	Memory buffer
SCB1_EZ_DATA174	0x406106B8	FULL	Memory buffer
SCB1_EZ_DATA175	0x406106BC	FULL	Memory buffer
SCB1_EZ_DATA176	0x406106C0	FULL	Memory buffer
SCB1_EZ_DATA177	0x406106C4	FULL	Memory buffer
SCB1_EZ_DATA178	0x406106C8	FULL	Memory buffer
SCB1_EZ_DATA179	0x406106CC	FULL	Memory buffer
SCB1_EZ_DATA180	0x406106D0	FULL	Memory buffer
SCB1_EZ_DATA181	0x406106D4	FULL	Memory buffer
SCB1_EZ_DATA182	0x406106D8	FULL	Memory buffer
SCB1_EZ_DATA183	0x406106DC	FULL	Memory buffer
SCB1_EZ_DATA184	0x406106E0	FULL	Memory buffer
SCB1_EZ_DATA185	0x406106E4	FULL	Memory buffer
SCB1_EZ_DATA186	0x406106E8	FULL	Memory buffer
SCB1_EZ_DATA187	0x406106EC	FULL	Memory buffer
SCB1_EZ_DATA188	0x406106F0	FULL	Memory buffer
SCB1_EZ_DATA189	0x406106F4	FULL	Memory buffer
SCB1_EZ_DATA190	0x406106F8	FULL	Memory buffer
SCB1_EZ_DATA191	0x406106FC	FULL	Memory buffer
SCB1_EZ_DATA192	0x40610700	FULL	Memory buffer
SCB1_EZ_DATA193	0x40610704	FULL	Memory buffer
SCB1_EZ_DATA194	0x40610708	FULL	Memory buffer
SCB1_EZ_DATA195	0x4061070C	FULL	Memory buffer
SCB1_EZ_DATA196	0x40610710	FULL	Memory buffer
SCB1_EZ_DATA197	0x40610714	FULL	Memory buffer
SCB1_EZ_DATA198	0x40610718	FULL	Memory buffer
SCB1_EZ_DATA199	0x4061071C	FULL	Memory buffer
SCB1_EZ_DATA200	0x40610720	FULL	Memory buffer
SCB1_EZ_DATA201	0x40610724	FULL	Memory buffer
SCB1_EZ_DATA202	0x40610728	FULL	Memory buffer
SCB1_EZ_DATA203	0x4061072C	FULL	Memory buffer
SCB1_EZ_DATA204	0x40610730	FULL	Memory buffer
SCB1_EZ_DATA205	0x40610734	FULL	Memory buffer
SCB1_EZ_DATA206	0x40610738	FULL	Memory buffer
SCB1_EZ_DATA207	0x4061073C	FULL	Memory buffer
SCB1_EZ_DATA208	0x40610740	FULL	Memory buffer
SCB1_EZ_DATA209	0x40610744	FULL	Memory buffer
SCB1_EZ_DATA210	0x40610748	FULL	Memory buffer
SCB1_EZ_DATA211	0x4061074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB1_EZ_DATA212	0x40610750	FULL	Memory buffer
SCB1_EZ_DATA213	0x40610754	FULL	Memory buffer
SCB1_EZ_DATA214	0x40610758	FULL	Memory buffer
SCB1_EZ_DATA215	0x4061075C	FULL	Memory buffer
SCB1_EZ_DATA216	0x40610760	FULL	Memory buffer
SCB1_EZ_DATA217	0x40610764	FULL	Memory buffer
SCB1_EZ_DATA218	0x40610768	FULL	Memory buffer
SCB1_EZ_DATA219	0x4061076C	FULL	Memory buffer
SCB1_EZ_DATA220	0x40610770	FULL	Memory buffer
SCB1_EZ_DATA221	0x40610774	FULL	Memory buffer
SCB1_EZ_DATA222	0x40610778	FULL	Memory buffer
SCB1_EZ_DATA223	0x4061077C	FULL	Memory buffer
SCB1_EZ_DATA224	0x40610780	FULL	Memory buffer
SCB1_EZ_DATA225	0x40610784	FULL	Memory buffer
SCB1_EZ_DATA226	0x40610788	FULL	Memory buffer
SCB1_EZ_DATA227	0x4061078C	FULL	Memory buffer
SCB1_EZ_DATA228	0x40610790	FULL	Memory buffer
SCB1_EZ_DATA229	0x40610794	FULL	Memory buffer
SCB1_EZ_DATA230	0x40610798	FULL	Memory buffer
SCB1_EZ_DATA231	0x4061079C	FULL	Memory buffer
SCB1_EZ_DATA232	0x406107A0	FULL	Memory buffer
SCB1_EZ_DATA233	0x406107A4	FULL	Memory buffer
SCB1_EZ_DATA234	0x406107A8	FULL	Memory buffer
SCB1_EZ_DATA235	0x406107AC	FULL	Memory buffer
SCB1_EZ_DATA236	0x406107B0	FULL	Memory buffer
SCB1_EZ_DATA237	0x406107B4	FULL	Memory buffer
SCB1_EZ_DATA238	0x406107B8	FULL	Memory buffer
SCB1_EZ_DATA239	0x406107BC	FULL	Memory buffer
SCB1_EZ_DATA240	0x406107C0	FULL	Memory buffer
SCB1_EZ_DATA241	0x406107C4	FULL	Memory buffer
SCB1_EZ_DATA242	0x406107C8	FULL	Memory buffer
SCB1_EZ_DATA243	0x406107CC	FULL	Memory buffer
SCB1_EZ_DATA244	0x406107D0	FULL	Memory buffer
SCB1_EZ_DATA245	0x406107D4	FULL	Memory buffer
SCB1_EZ_DATA246	0x406107D8	FULL	Memory buffer
SCB1_EZ_DATA247	0x406107DC	FULL	Memory buffer
SCB1_EZ_DATA248	0x406107E0	FULL	Memory buffer
SCB1_EZ_DATA249	0x406107E4	FULL	Memory buffer
SCB1_EZ_DATA250	0x406107E8	FULL	Memory buffer
SCB1_EZ_DATA251	0x406107EC	FULL	Memory buffer
SCB1_EZ_DATA252	0x406107F0	FULL	Memory buffer
SCB1_EZ_DATA253	0x406107F4	FULL	Memory buffer
SCB1_EZ_DATA254	0x406107F8	FULL	Memory buffer
SCB1_EZ_DATA255	0x406107FC	FULL	Memory buffer
SCB1_INTR_CAUSE	0x40610E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB1_INTR_SPI_EC	0x40610EC0	FULL	Externally clocked SPI interrupt request
SCB1_INTR_SPI_EC_MASK	0x40610EC8	FULL	Externally clocked SPI interrupt mask
SCB1_INTR_SPI_EC_MASKED	0x40610ECC	FULL	Externally clocked SPI interrupt masked
SCB1_INTR_M	0x40610F00	FULL	Master interrupt request
SCB1_INTR_M_SET	0x40610F04	FULL	Master interrupt set request
SCB1_INTR_M_MASK	0x40610F08	FULL	Master interrupt mask
SCB1_INTR_M_MASKED	0x40610F0C	FULL	Master interrupt masked request
SCB1_INTR_S	0x40610F40	FULL	Slave interrupt request
SCB1_INTR_S_SET	0x40610F44	FULL	Slave interrupt set request
SCB1_INTR_S_MASK	0x40610F48	FULL	Slave interrupt mask
SCB1_INTR_S_MASKED	0x40610F4C	FULL	Slave interrupt masked request
SCB1_INTR_TX	0x40610F80	FULL	Transmitter interrupt request
SCB1_INTR_TX_SET	0x40610F84	FULL	Transmitter interrupt set request
SCB1_INTR_TX_MASK	0x40610F88	FULL	Transmitter interrupt mask
SCB1_INTR_TX_MASKED	0x40610F8C	FULL	Transmitter interrupt masked request
SCB1_INTR_RX	0x40610FC0	FULL	Receiver interrupt request
SCB1_INTR_RX_SET	0x40610FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB1_INTR_RX_MASK	0x40610FC8	FULL	Receiver interrupt mask
SCB1_INTR_RX_MASKED	0x40610FCC	FULL	Receiver interrupt masked request

24.3 SCB 2

Description Serial Communications Block
(SPI/UART/I2C)
Base Address 0x40620000
Size 0x10000
Slave Num MMIO6 - 2

Register Name	Address	Permission	Description
SCB2_CTRL	0x40620000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB2_STATUS	0x40620004	FULL	Generic status
SCB2_SPI_CTRL	0x40620020	FULL	SPI control
SCB2_SPI_STATUS	0x40620024	FULL	SPI status
SCB2_SPI_TX_CTRL	0x40620028	FULL	SPI transmitter control
SCB2_SPI_RX_CTRL	0x4062002C	FULL	SPI receiver control
SCB2_UART_CTRL	0x40620040	FULL	UART control
SCB2_UART_TX_CTRL	0x40620044	FULL	UART transmitter control
SCB2_UART_RX_CTRL	0x40620048	FULL	UART receiver control
SCB2_UART_RX_STATUS	0x4062004C	FULL	UART receiver status
SCB2_UART_FLOW_CTRL	0x40620050	FULL	UART flow control
SCB2_I2C_CTRL	0x40620060	FULL	I2C control
SCB2_I2C_STATUS	0x40620064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB2_I2C_M_CMD	0x40620068	FULL	I2C master command
SCB2_I2C_S_CMD	0x4062006C	FULL	I2C slave command
SCB2_I2C_CFG	0x40620070	FULL	I2C configuration
SCB2_TX_CTRL	0x40620200	FULL	Transmitter control
SCB2_TX_FIFO_CTRL	0x40620204	FULL	Transmitter FIFO control
SCB2_TX_FIFO_STATUS	0x40620208	FULL	Transmitter FIFO status
SCB2_TX_FIFO_WR	0x40620240	FULL	Transmitter FIFO write
SCB2_RX_CTRL	0x40620300	FULL	Receiver control
SCB2_RX_FIFO_CTRL	0x40620304	FULL	Receiver FIFO control
SCB2_RX_FIFO_STATUS	0x40620308	FULL	Receiver FIFO status
SCB2_RX_MATCH	0x40620310	FULL	Slave address and mask
SCB2_RX_FIFO_RD	0x40620340	FULL	Receiver FIFO read
SCB2_RX_FIFO_RD_SILENT	0x40620344	FULL	Receiver FIFO read silent
SCB2_EZ_DATA0	0x40620400	FULL	Memory buffer
SCB2_EZ_DATA1	0x40620404	FULL	Memory buffer
SCB2_EZ_DATA2	0x40620408	FULL	Memory buffer
SCB2_EZ_DATA3	0x4062040C	FULL	Memory buffer
SCB2_EZ_DATA4	0x40620410	FULL	Memory buffer
SCB2_EZ_DATA5	0x40620414	FULL	Memory buffer
SCB2_EZ_DATA6	0x40620418	FULL	Memory buffer
SCB2_EZ_DATA7	0x4062041C	FULL	Memory buffer
SCB2_EZ_DATA8	0x40620420	FULL	Memory buffer
SCB2_EZ_DATA9	0x40620424	FULL	Memory buffer
SCB2_EZ_DATA10	0x40620428	FULL	Memory buffer
SCB2_EZ_DATA11	0x4062042C	FULL	Memory buffer
SCB2_EZ_DATA12	0x40620430	FULL	Memory buffer
SCB2_EZ_DATA13	0x40620434	FULL	Memory buffer
SCB2_EZ_DATA14	0x40620438	FULL	Memory buffer
SCB2_EZ_DATA15	0x4062043C	FULL	Memory buffer
SCB2_EZ_DATA16	0x40620440	FULL	Memory buffer
SCB2_EZ_DATA17	0x40620444	FULL	Memory buffer
SCB2_EZ_DATA18	0x40620448	FULL	Memory buffer
SCB2_EZ_DATA19	0x4062044C	FULL	Memory buffer
SCB2_EZ_DATA20	0x40620450	FULL	Memory buffer
SCB2_EZ_DATA21	0x40620454	FULL	Memory buffer
SCB2_EZ_DATA22	0x40620458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB2_EZ_DATA23	0x4062045C	FULL	Memory buffer
SCB2_EZ_DATA24	0x40620460	FULL	Memory buffer
SCB2_EZ_DATA25	0x40620464	FULL	Memory buffer
SCB2_EZ_DATA26	0x40620468	FULL	Memory buffer
SCB2_EZ_DATA27	0x4062046C	FULL	Memory buffer
SCB2_EZ_DATA28	0x40620470	FULL	Memory buffer
SCB2_EZ_DATA29	0x40620474	FULL	Memory buffer
SCB2_EZ_DATA30	0x40620478	FULL	Memory buffer
SCB2_EZ_DATA31	0x4062047C	FULL	Memory buffer
SCB2_EZ_DATA32	0x40620480	FULL	Memory buffer
SCB2_EZ_DATA33	0x40620484	FULL	Memory buffer
SCB2_EZ_DATA34	0x40620488	FULL	Memory buffer
SCB2_EZ_DATA35	0x4062048C	FULL	Memory buffer
SCB2_EZ_DATA36	0x40620490	FULL	Memory buffer
SCB2_EZ_DATA37	0x40620494	FULL	Memory buffer
SCB2_EZ_DATA38	0x40620498	FULL	Memory buffer
SCB2_EZ_DATA39	0x4062049C	FULL	Memory buffer
SCB2_EZ_DATA40	0x406204A0	FULL	Memory buffer
SCB2_EZ_DATA41	0x406204A4	FULL	Memory buffer
SCB2_EZ_DATA42	0x406204A8	FULL	Memory buffer
SCB2_EZ_DATA43	0x406204AC	FULL	Memory buffer
SCB2_EZ_DATA44	0x406204B0	FULL	Memory buffer
SCB2_EZ_DATA45	0x406204B4	FULL	Memory buffer
SCB2_EZ_DATA46	0x406204B8	FULL	Memory buffer
SCB2_EZ_DATA47	0x406204BC	FULL	Memory buffer
SCB2_EZ_DATA48	0x406204C0	FULL	Memory buffer
SCB2_EZ_DATA49	0x406204C4	FULL	Memory buffer
SCB2_EZ_DATA50	0x406204C8	FULL	Memory buffer
SCB2_EZ_DATA51	0x406204CC	FULL	Memory buffer
SCB2_EZ_DATA52	0x406204D0	FULL	Memory buffer
SCB2_EZ_DATA53	0x406204D4	FULL	Memory buffer
SCB2_EZ_DATA54	0x406204D8	FULL	Memory buffer
SCB2_EZ_DATA55	0x406204DC	FULL	Memory buffer
SCB2_EZ_DATA56	0x406204E0	FULL	Memory buffer
SCB2_EZ_DATA57	0x406204E4	FULL	Memory buffer
SCB2_EZ_DATA58	0x406204E8	FULL	Memory buffer
SCB2_EZ_DATA59	0x406204EC	FULL	Memory buffer
SCB2_EZ_DATA60	0x406204F0	FULL	Memory buffer
SCB2_EZ_DATA61	0x406204F4	FULL	Memory buffer
SCB2_EZ_DATA62	0x406204F8	FULL	Memory buffer
SCB2_EZ_DATA63	0x406204FC	FULL	Memory buffer
SCB2_EZ_DATA64	0x40620500	FULL	Memory buffer
SCB2_EZ_DATA65	0x40620504	FULL	Memory buffer
SCB2_EZ_DATA66	0x40620508	FULL	Memory buffer
SCB2_EZ_DATA67	0x4062050C	FULL	Memory buffer
SCB2_EZ_DATA68	0x40620510	FULL	Memory buffer
SCB2_EZ_DATA69	0x40620514	FULL	Memory buffer
SCB2_EZ_DATA70	0x40620518	FULL	Memory buffer
SCB2_EZ_DATA71	0x4062051C	FULL	Memory buffer
SCB2_EZ_DATA72	0x40620520	FULL	Memory buffer
SCB2_EZ_DATA73	0x40620524	FULL	Memory buffer
SCB2_EZ_DATA74	0x40620528	FULL	Memory buffer
SCB2_EZ_DATA75	0x4062052C	FULL	Memory buffer
SCB2_EZ_DATA76	0x40620530	FULL	Memory buffer
SCB2_EZ_DATA77	0x40620534	FULL	Memory buffer
SCB2_EZ_DATA78	0x40620538	FULL	Memory buffer
SCB2_EZ_DATA79	0x4062053C	FULL	Memory buffer
SCB2_EZ_DATA80	0x40620540	FULL	Memory buffer
SCB2_EZ_DATA81	0x40620544	FULL	Memory buffer
SCB2_EZ_DATA82	0x40620548	FULL	Memory buffer
SCB2_EZ_DATA83	0x4062054C	FULL	Memory buffer
SCB2_EZ_DATA84	0x40620550	FULL	Memory buffer
SCB2_EZ_DATA85	0x40620554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB2_EZ_DATA86	0x40620558	FULL	Memory buffer
SCB2_EZ_DATA87	0x4062055C	FULL	Memory buffer
SCB2_EZ_DATA88	0x40620560	FULL	Memory buffer
SCB2_EZ_DATA89	0x40620564	FULL	Memory buffer
SCB2_EZ_DATA90	0x40620568	FULL	Memory buffer
SCB2_EZ_DATA91	0x4062056C	FULL	Memory buffer
SCB2_EZ_DATA92	0x40620570	FULL	Memory buffer
SCB2_EZ_DATA93	0x40620574	FULL	Memory buffer
SCB2_EZ_DATA94	0x40620578	FULL	Memory buffer
SCB2_EZ_DATA95	0x4062057C	FULL	Memory buffer
SCB2_EZ_DATA96	0x40620580	FULL	Memory buffer
SCB2_EZ_DATA97	0x40620584	FULL	Memory buffer
SCB2_EZ_DATA98	0x40620588	FULL	Memory buffer
SCB2_EZ_DATA99	0x4062058C	FULL	Memory buffer
SCB2_EZ_DATA100	0x40620590	FULL	Memory buffer
SCB2_EZ_DATA101	0x40620594	FULL	Memory buffer
SCB2_EZ_DATA102	0x40620598	FULL	Memory buffer
SCB2_EZ_DATA103	0x4062059C	FULL	Memory buffer
SCB2_EZ_DATA104	0x406205A0	FULL	Memory buffer
SCB2_EZ_DATA105	0x406205A4	FULL	Memory buffer
SCB2_EZ_DATA106	0x406205A8	FULL	Memory buffer
SCB2_EZ_DATA107	0x406205AC	FULL	Memory buffer
SCB2_EZ_DATA108	0x406205B0	FULL	Memory buffer
SCB2_EZ_DATA109	0x406205B4	FULL	Memory buffer
SCB2_EZ_DATA110	0x406205B8	FULL	Memory buffer
SCB2_EZ_DATA111	0x406205BC	FULL	Memory buffer
SCB2_EZ_DATA112	0x406205C0	FULL	Memory buffer
SCB2_EZ_DATA113	0x406205C4	FULL	Memory buffer
SCB2_EZ_DATA114	0x406205C8	FULL	Memory buffer
SCB2_EZ_DATA115	0x406205CC	FULL	Memory buffer
SCB2_EZ_DATA116	0x406205D0	FULL	Memory buffer
SCB2_EZ_DATA117	0x406205D4	FULL	Memory buffer
SCB2_EZ_DATA118	0x406205D8	FULL	Memory buffer
SCB2_EZ_DATA119	0x406205DC	FULL	Memory buffer
SCB2_EZ_DATA120	0x406205E0	FULL	Memory buffer
SCB2_EZ_DATA121	0x406205E4	FULL	Memory buffer
SCB2_EZ_DATA122	0x406205E8	FULL	Memory buffer
SCB2_EZ_DATA123	0x406205EC	FULL	Memory buffer
SCB2_EZ_DATA124	0x406205F0	FULL	Memory buffer
SCB2_EZ_DATA125	0x406205F4	FULL	Memory buffer
SCB2_EZ_DATA126	0x406205F8	FULL	Memory buffer
SCB2_EZ_DATA127	0x406205FC	FULL	Memory buffer
SCB2_EZ_DATA128	0x40620600	FULL	Memory buffer
SCB2_EZ_DATA129	0x40620604	FULL	Memory buffer
SCB2_EZ_DATA130	0x40620608	FULL	Memory buffer
SCB2_EZ_DATA131	0x4062060C	FULL	Memory buffer
SCB2_EZ_DATA132	0x40620610	FULL	Memory buffer
SCB2_EZ_DATA133	0x40620614	FULL	Memory buffer
SCB2_EZ_DATA134	0x40620618	FULL	Memory buffer
SCB2_EZ_DATA135	0x4062061C	FULL	Memory buffer
SCB2_EZ_DATA136	0x40620620	FULL	Memory buffer
SCB2_EZ_DATA137	0x40620624	FULL	Memory buffer
SCB2_EZ_DATA138	0x40620628	FULL	Memory buffer
SCB2_EZ_DATA139	0x4062062C	FULL	Memory buffer
SCB2_EZ_DATA140	0x40620630	FULL	Memory buffer
SCB2_EZ_DATA141	0x40620634	FULL	Memory buffer
SCB2_EZ_DATA142	0x40620638	FULL	Memory buffer
SCB2_EZ_DATA143	0x4062063C	FULL	Memory buffer
SCB2_EZ_DATA144	0x40620640	FULL	Memory buffer
SCB2_EZ_DATA145	0x40620644	FULL	Memory buffer
SCB2_EZ_DATA146	0x40620648	FULL	Memory buffer
SCB2_EZ_DATA147	0x4062064C	FULL	Memory buffer
SCB2_EZ_DATA148	0x40620650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB2_EZ_DATA149	0x40620654	FULL	Memory buffer
SCB2_EZ_DATA150	0x40620658	FULL	Memory buffer
SCB2_EZ_DATA151	0x4062065C	FULL	Memory buffer
SCB2_EZ_DATA152	0x40620660	FULL	Memory buffer
SCB2_EZ_DATA153	0x40620664	FULL	Memory buffer
SCB2_EZ_DATA154	0x40620668	FULL	Memory buffer
SCB2_EZ_DATA155	0x4062066C	FULL	Memory buffer
SCB2_EZ_DATA156	0x40620670	FULL	Memory buffer
SCB2_EZ_DATA157	0x40620674	FULL	Memory buffer
SCB2_EZ_DATA158	0x40620678	FULL	Memory buffer
SCB2_EZ_DATA159	0x4062067C	FULL	Memory buffer
SCB2_EZ_DATA160	0x40620680	FULL	Memory buffer
SCB2_EZ_DATA161	0x40620684	FULL	Memory buffer
SCB2_EZ_DATA162	0x40620688	FULL	Memory buffer
SCB2_EZ_DATA163	0x4062068C	FULL	Memory buffer
SCB2_EZ_DATA164	0x40620690	FULL	Memory buffer
SCB2_EZ_DATA165	0x40620694	FULL	Memory buffer
SCB2_EZ_DATA166	0x40620698	FULL	Memory buffer
SCB2_EZ_DATA167	0x4062069C	FULL	Memory buffer
SCB2_EZ_DATA168	0x406206A0	FULL	Memory buffer
SCB2_EZ_DATA169	0x406206A4	FULL	Memory buffer
SCB2_EZ_DATA170	0x406206A8	FULL	Memory buffer
SCB2_EZ_DATA171	0x406206AC	FULL	Memory buffer
SCB2_EZ_DATA172	0x406206B0	FULL	Memory buffer
SCB2_EZ_DATA173	0x406206B4	FULL	Memory buffer
SCB2_EZ_DATA174	0x406206B8	FULL	Memory buffer
SCB2_EZ_DATA175	0x406206BC	FULL	Memory buffer
SCB2_EZ_DATA176	0x406206C0	FULL	Memory buffer
SCB2_EZ_DATA177	0x406206C4	FULL	Memory buffer
SCB2_EZ_DATA178	0x406206C8	FULL	Memory buffer
SCB2_EZ_DATA179	0x406206CC	FULL	Memory buffer
SCB2_EZ_DATA180	0x406206D0	FULL	Memory buffer
SCB2_EZ_DATA181	0x406206D4	FULL	Memory buffer
SCB2_EZ_DATA182	0x406206D8	FULL	Memory buffer
SCB2_EZ_DATA183	0x406206DC	FULL	Memory buffer
SCB2_EZ_DATA184	0x406206E0	FULL	Memory buffer
SCB2_EZ_DATA185	0x406206E4	FULL	Memory buffer
SCB2_EZ_DATA186	0x406206E8	FULL	Memory buffer
SCB2_EZ_DATA187	0x406206EC	FULL	Memory buffer
SCB2_EZ_DATA188	0x406206F0	FULL	Memory buffer
SCB2_EZ_DATA189	0x406206F4	FULL	Memory buffer
SCB2_EZ_DATA190	0x406206F8	FULL	Memory buffer
SCB2_EZ_DATA191	0x406206FC	FULL	Memory buffer
SCB2_EZ_DATA192	0x40620700	FULL	Memory buffer
SCB2_EZ_DATA193	0x40620704	FULL	Memory buffer
SCB2_EZ_DATA194	0x40620708	FULL	Memory buffer
SCB2_EZ_DATA195	0x4062070C	FULL	Memory buffer
SCB2_EZ_DATA196	0x40620710	FULL	Memory buffer
SCB2_EZ_DATA197	0x40620714	FULL	Memory buffer
SCB2_EZ_DATA198	0x40620718	FULL	Memory buffer
SCB2_EZ_DATA199	0x4062071C	FULL	Memory buffer
SCB2_EZ_DATA200	0x40620720	FULL	Memory buffer
SCB2_EZ_DATA201	0x40620724	FULL	Memory buffer
SCB2_EZ_DATA202	0x40620728	FULL	Memory buffer
SCB2_EZ_DATA203	0x4062072C	FULL	Memory buffer
SCB2_EZ_DATA204	0x40620730	FULL	Memory buffer
SCB2_EZ_DATA205	0x40620734	FULL	Memory buffer
SCB2_EZ_DATA206	0x40620738	FULL	Memory buffer
SCB2_EZ_DATA207	0x4062073C	FULL	Memory buffer
SCB2_EZ_DATA208	0x40620740	FULL	Memory buffer
SCB2_EZ_DATA209	0x40620744	FULL	Memory buffer
SCB2_EZ_DATA210	0x40620748	FULL	Memory buffer
SCB2_EZ_DATA211	0x4062074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB2_EZ_DATA212	0x40620750	FULL	Memory buffer
SCB2_EZ_DATA213	0x40620754	FULL	Memory buffer
SCB2_EZ_DATA214	0x40620758	FULL	Memory buffer
SCB2_EZ_DATA215	0x4062075C	FULL	Memory buffer
SCB2_EZ_DATA216	0x40620760	FULL	Memory buffer
SCB2_EZ_DATA217	0x40620764	FULL	Memory buffer
SCB2_EZ_DATA218	0x40620768	FULL	Memory buffer
SCB2_EZ_DATA219	0x4062076C	FULL	Memory buffer
SCB2_EZ_DATA220	0x40620770	FULL	Memory buffer
SCB2_EZ_DATA221	0x40620774	FULL	Memory buffer
SCB2_EZ_DATA222	0x40620778	FULL	Memory buffer
SCB2_EZ_DATA223	0x4062077C	FULL	Memory buffer
SCB2_EZ_DATA224	0x40620780	FULL	Memory buffer
SCB2_EZ_DATA225	0x40620784	FULL	Memory buffer
SCB2_EZ_DATA226	0x40620788	FULL	Memory buffer
SCB2_EZ_DATA227	0x4062078C	FULL	Memory buffer
SCB2_EZ_DATA228	0x40620790	FULL	Memory buffer
SCB2_EZ_DATA229	0x40620794	FULL	Memory buffer
SCB2_EZ_DATA230	0x40620798	FULL	Memory buffer
SCB2_EZ_DATA231	0x4062079C	FULL	Memory buffer
SCB2_EZ_DATA232	0x406207A0	FULL	Memory buffer
SCB2_EZ_DATA233	0x406207A4	FULL	Memory buffer
SCB2_EZ_DATA234	0x406207A8	FULL	Memory buffer
SCB2_EZ_DATA235	0x406207AC	FULL	Memory buffer
SCB2_EZ_DATA236	0x406207B0	FULL	Memory buffer
SCB2_EZ_DATA237	0x406207B4	FULL	Memory buffer
SCB2_EZ_DATA238	0x406207B8	FULL	Memory buffer
SCB2_EZ_DATA239	0x406207BC	FULL	Memory buffer
SCB2_EZ_DATA240	0x406207C0	FULL	Memory buffer
SCB2_EZ_DATA241	0x406207C4	FULL	Memory buffer
SCB2_EZ_DATA242	0x406207C8	FULL	Memory buffer
SCB2_EZ_DATA243	0x406207CC	FULL	Memory buffer
SCB2_EZ_DATA244	0x406207D0	FULL	Memory buffer
SCB2_EZ_DATA245	0x406207D4	FULL	Memory buffer
SCB2_EZ_DATA246	0x406207D8	FULL	Memory buffer
SCB2_EZ_DATA247	0x406207DC	FULL	Memory buffer
SCB2_EZ_DATA248	0x406207E0	FULL	Memory buffer
SCB2_EZ_DATA249	0x406207E4	FULL	Memory buffer
SCB2_EZ_DATA250	0x406207E8	FULL	Memory buffer
SCB2_EZ_DATA251	0x406207EC	FULL	Memory buffer
SCB2_EZ_DATA252	0x406207F0	FULL	Memory buffer
SCB2_EZ_DATA253	0x406207F4	FULL	Memory buffer
SCB2_EZ_DATA254	0x406207F8	FULL	Memory buffer
SCB2_EZ_DATA255	0x406207FC	FULL	Memory buffer
SCB2_INTR_CAUSE	0x40620E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB2_INTR_SPI_EC	0x40620EC0	FULL	Externally clocked SPI interrupt request
SCB2_INTR_SPI_EC_MASK	0x40620EC8	FULL	Externally clocked SPI interrupt mask
SCB2_INTR_SPI_EC_MASKED	0x40620ECC	FULL	Externally clocked SPI interrupt masked
SCB2_INTR_M	0x40620F00	FULL	Master interrupt request
SCB2_INTR_M_SET	0x40620F04	FULL	Master interrupt set request
SCB2_INTR_M_MASK	0x40620F08	FULL	Master interrupt mask
SCB2_INTR_M_MASKED	0x40620F0C	FULL	Master interrupt masked request
SCB2_INTR_S	0x40620F40	FULL	Slave interrupt request
SCB2_INTR_S_SET	0x40620F44	FULL	Slave interrupt set request
SCB2_INTR_S_MASK	0x40620F48	FULL	Slave interrupt mask
SCB2_INTR_S_MASKED	0x40620F4C	FULL	Slave interrupt masked request
SCB2_INTR_TX	0x40620F80	FULL	Transmitter interrupt request
SCB2_INTR_TX_SET	0x40620F84	FULL	Transmitter interrupt set request
SCB2_INTR_TX_MASK	0x40620F88	FULL	Transmitter interrupt mask
SCB2_INTR_TX_MASKED	0x40620F8C	FULL	Transmitter interrupt masked request
SCB2_INTR_RX	0x40620FC0	FULL	Receiver interrupt request
SCB2_INTR_RX_SET	0x40620FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB2_INTR_RX_MASK	0x40620FC8	FULL	Receiver interrupt mask
SCB2_INTR_RX_MASKED	0x40620FCC	FULL	Receiver interrupt masked request

24.4 SCB 3

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40630000

Size 0x10000

Slave Num MMIO6 - 3

Register Name	Address	Permission	Description
SCB3_CTRL	0x40630000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB3_STATUS	0x40630004	FULL	Generic status
SCB3_SPI_CTRL	0x40630020	FULL	SPI control
SCB3_SPI_STATUS	0x40630024	FULL	SPI status
SCB3_SPI_TX_CTRL	0x40630028	FULL	SPI transmitter control
SCB3_SPI_RX_CTRL	0x4063002C	FULL	SPI receiver control
SCB3_UART_CTRL	0x40630040	FULL	UART control
SCB3_UART_TX_CTRL	0x40630044	FULL	UART transmitter control
SCB3_UART_RX_CTRL	0x40630048	FULL	UART receiver control
SCB3_UART_RX_STATUS	0x4063004C	FULL	UART receiver status
SCB3_UART_FLOW_CTRL	0x40630050	FULL	UART flow control
SCB3_I2C_CTRL	0x40630060	FULL	I2C control
SCB3_I2C_STATUS	0x40630064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB3_I2C_M_CMD	0x40630068	FULL	I2C master command
SCB3_I2C_S_CMD	0x4063006C	FULL	I2C slave command
SCB3_I2C_CFG	0x40630070	FULL	I2C configuration
SCB3_TX_CTRL	0x40630200	FULL	Transmitter control
SCB3_TX_FIFO_CTRL	0x40630204	FULL	Transmitter FIFO control
SCB3_TX_FIFO_STATUS	0x40630208	FULL	Transmitter FIFO status
SCB3_TX_FIFO_WR	0x40630240	FULL	Transmitter FIFO write
SCB3_RX_CTRL	0x40630300	FULL	Receiver control
SCB3_RX_FIFO_CTRL	0x40630304	FULL	Receiver FIFO control
SCB3_RX_FIFO_STATUS	0x40630308	FULL	Receiver FIFO status
SCB3_RX_MATCH	0x40630310	FULL	Slave address and mask
SCB3_RX_FIFO_RD	0x40630340	FULL	Receiver FIFO read
SCB3_RX_FIFO_RD_SILENT	0x40630344	FULL	Receiver FIFO read silent
SCB3_EZ_DATA0	0x40630400	FULL	Memory buffer
SCB3_EZ_DATA1	0x40630404	FULL	Memory buffer
SCB3_EZ_DATA2	0x40630408	FULL	Memory buffer
SCB3_EZ_DATA3	0x4063040C	FULL	Memory buffer
SCB3_EZ_DATA4	0x40630410	FULL	Memory buffer
SCB3_EZ_DATA5	0x40630414	FULL	Memory buffer
SCB3_EZ_DATA6	0x40630418	FULL	Memory buffer
SCB3_EZ_DATA7	0x4063041C	FULL	Memory buffer
SCB3_EZ_DATA8	0x40630420	FULL	Memory buffer
SCB3_EZ_DATA9	0x40630424	FULL	Memory buffer
SCB3_EZ_DATA10	0x40630428	FULL	Memory buffer
SCB3_EZ_DATA11	0x4063042C	FULL	Memory buffer
SCB3_EZ_DATA12	0x40630430	FULL	Memory buffer
SCB3_EZ_DATA13	0x40630434	FULL	Memory buffer
SCB3_EZ_DATA14	0x40630438	FULL	Memory buffer
SCB3_EZ_DATA15	0x4063043C	FULL	Memory buffer
SCB3_EZ_DATA16	0x40630440	FULL	Memory buffer
SCB3_EZ_DATA17	0x40630444	FULL	Memory buffer
SCB3_EZ_DATA18	0x40630448	FULL	Memory buffer
SCB3_EZ_DATA19	0x4063044C	FULL	Memory buffer
SCB3_EZ_DATA20	0x40630450	FULL	Memory buffer
SCB3_EZ_DATA21	0x40630454	FULL	Memory buffer
SCB3_EZ_DATA22	0x40630458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB3_EZ_DATA23	0x4063045C	FULL	Memory buffer
SCB3_EZ_DATA24	0x40630460	FULL	Memory buffer
SCB3_EZ_DATA25	0x40630464	FULL	Memory buffer
SCB3_EZ_DATA26	0x40630468	FULL	Memory buffer
SCB3_EZ_DATA27	0x4063046C	FULL	Memory buffer
SCB3_EZ_DATA28	0x40630470	FULL	Memory buffer
SCB3_EZ_DATA29	0x40630474	FULL	Memory buffer
SCB3_EZ_DATA30	0x40630478	FULL	Memory buffer
SCB3_EZ_DATA31	0x4063047C	FULL	Memory buffer
SCB3_EZ_DATA32	0x40630480	FULL	Memory buffer
SCB3_EZ_DATA33	0x40630484	FULL	Memory buffer
SCB3_EZ_DATA34	0x40630488	FULL	Memory buffer
SCB3_EZ_DATA35	0x4063048C	FULL	Memory buffer
SCB3_EZ_DATA36	0x40630490	FULL	Memory buffer
SCB3_EZ_DATA37	0x40630494	FULL	Memory buffer
SCB3_EZ_DATA38	0x40630498	FULL	Memory buffer
SCB3_EZ_DATA39	0x4063049C	FULL	Memory buffer
SCB3_EZ_DATA40	0x406304A0	FULL	Memory buffer
SCB3_EZ_DATA41	0x406304A4	FULL	Memory buffer
SCB3_EZ_DATA42	0x406304A8	FULL	Memory buffer
SCB3_EZ_DATA43	0x406304AC	FULL	Memory buffer
SCB3_EZ_DATA44	0x406304B0	FULL	Memory buffer
SCB3_EZ_DATA45	0x406304B4	FULL	Memory buffer
SCB3_EZ_DATA46	0x406304B8	FULL	Memory buffer
SCB3_EZ_DATA47	0x406304BC	FULL	Memory buffer
SCB3_EZ_DATA48	0x406304C0	FULL	Memory buffer
SCB3_EZ_DATA49	0x406304C4	FULL	Memory buffer
SCB3_EZ_DATA50	0x406304C8	FULL	Memory buffer
SCB3_EZ_DATA51	0x406304CC	FULL	Memory buffer
SCB3_EZ_DATA52	0x406304D0	FULL	Memory buffer
SCB3_EZ_DATA53	0x406304D4	FULL	Memory buffer
SCB3_EZ_DATA54	0x406304D8	FULL	Memory buffer
SCB3_EZ_DATA55	0x406304DC	FULL	Memory buffer
SCB3_EZ_DATA56	0x406304E0	FULL	Memory buffer
SCB3_EZ_DATA57	0x406304E4	FULL	Memory buffer
SCB3_EZ_DATA58	0x406304E8	FULL	Memory buffer
SCB3_EZ_DATA59	0x406304EC	FULL	Memory buffer
SCB3_EZ_DATA60	0x406304F0	FULL	Memory buffer
SCB3_EZ_DATA61	0x406304F4	FULL	Memory buffer
SCB3_EZ_DATA62	0x406304F8	FULL	Memory buffer
SCB3_EZ_DATA63	0x406304FC	FULL	Memory buffer
SCB3_EZ_DATA64	0x40630500	FULL	Memory buffer
SCB3_EZ_DATA65	0x40630504	FULL	Memory buffer
SCB3_EZ_DATA66	0x40630508	FULL	Memory buffer
SCB3_EZ_DATA67	0x4063050C	FULL	Memory buffer
SCB3_EZ_DATA68	0x40630510	FULL	Memory buffer
SCB3_EZ_DATA69	0x40630514	FULL	Memory buffer
SCB3_EZ_DATA70	0x40630518	FULL	Memory buffer
SCB3_EZ_DATA71	0x4063051C	FULL	Memory buffer
SCB3_EZ_DATA72	0x40630520	FULL	Memory buffer
SCB3_EZ_DATA73	0x40630524	FULL	Memory buffer
SCB3_EZ_DATA74	0x40630528	FULL	Memory buffer
SCB3_EZ_DATA75	0x4063052C	FULL	Memory buffer
SCB3_EZ_DATA76	0x40630530	FULL	Memory buffer
SCB3_EZ_DATA77	0x40630534	FULL	Memory buffer
SCB3_EZ_DATA78	0x40630538	FULL	Memory buffer
SCB3_EZ_DATA79	0x4063053C	FULL	Memory buffer
SCB3_EZ_DATA80	0x40630540	FULL	Memory buffer
SCB3_EZ_DATA81	0x40630544	FULL	Memory buffer
SCB3_EZ_DATA82	0x40630548	FULL	Memory buffer
SCB3_EZ_DATA83	0x4063054C	FULL	Memory buffer
SCB3_EZ_DATA84	0x40630550	FULL	Memory buffer
SCB3_EZ_DATA85	0x40630554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB3_EZ_DATA86	0x40630558	FULL	Memory buffer
SCB3_EZ_DATA87	0x4063055C	FULL	Memory buffer
SCB3_EZ_DATA88	0x40630560	FULL	Memory buffer
SCB3_EZ_DATA89	0x40630564	FULL	Memory buffer
SCB3_EZ_DATA90	0x40630568	FULL	Memory buffer
SCB3_EZ_DATA91	0x4063056C	FULL	Memory buffer
SCB3_EZ_DATA92	0x40630570	FULL	Memory buffer
SCB3_EZ_DATA93	0x40630574	FULL	Memory buffer
SCB3_EZ_DATA94	0x40630578	FULL	Memory buffer
SCB3_EZ_DATA95	0x4063057C	FULL	Memory buffer
SCB3_EZ_DATA96	0x40630580	FULL	Memory buffer
SCB3_EZ_DATA97	0x40630584	FULL	Memory buffer
SCB3_EZ_DATA98	0x40630588	FULL	Memory buffer
SCB3_EZ_DATA99	0x4063058C	FULL	Memory buffer
SCB3_EZ_DATA100	0x40630590	FULL	Memory buffer
SCB3_EZ_DATA101	0x40630594	FULL	Memory buffer
SCB3_EZ_DATA102	0x40630598	FULL	Memory buffer
SCB3_EZ_DATA103	0x4063059C	FULL	Memory buffer
SCB3_EZ_DATA104	0x406305A0	FULL	Memory buffer
SCB3_EZ_DATA105	0x406305A4	FULL	Memory buffer
SCB3_EZ_DATA106	0x406305A8	FULL	Memory buffer
SCB3_EZ_DATA107	0x406305AC	FULL	Memory buffer
SCB3_EZ_DATA108	0x406305B0	FULL	Memory buffer
SCB3_EZ_DATA109	0x406305B4	FULL	Memory buffer
SCB3_EZ_DATA110	0x406305B8	FULL	Memory buffer
SCB3_EZ_DATA111	0x406305BC	FULL	Memory buffer
SCB3_EZ_DATA112	0x406305C0	FULL	Memory buffer
SCB3_EZ_DATA113	0x406305C4	FULL	Memory buffer
SCB3_EZ_DATA114	0x406305C8	FULL	Memory buffer
SCB3_EZ_DATA115	0x406305CC	FULL	Memory buffer
SCB3_EZ_DATA116	0x406305D0	FULL	Memory buffer
SCB3_EZ_DATA117	0x406305D4	FULL	Memory buffer
SCB3_EZ_DATA118	0x406305D8	FULL	Memory buffer
SCB3_EZ_DATA119	0x406305DC	FULL	Memory buffer
SCB3_EZ_DATA120	0x406305E0	FULL	Memory buffer
SCB3_EZ_DATA121	0x406305E4	FULL	Memory buffer
SCB3_EZ_DATA122	0x406305E8	FULL	Memory buffer
SCB3_EZ_DATA123	0x406305EC	FULL	Memory buffer
SCB3_EZ_DATA124	0x406305F0	FULL	Memory buffer
SCB3_EZ_DATA125	0x406305F4	FULL	Memory buffer
SCB3_EZ_DATA126	0x406305F8	FULL	Memory buffer
SCB3_EZ_DATA127	0x406305FC	FULL	Memory buffer
SCB3_EZ_DATA128	0x40630600	FULL	Memory buffer
SCB3_EZ_DATA129	0x40630604	FULL	Memory buffer
SCB3_EZ_DATA130	0x40630608	FULL	Memory buffer
SCB3_EZ_DATA131	0x4063060C	FULL	Memory buffer
SCB3_EZ_DATA132	0x40630610	FULL	Memory buffer
SCB3_EZ_DATA133	0x40630614	FULL	Memory buffer
SCB3_EZ_DATA134	0x40630618	FULL	Memory buffer
SCB3_EZ_DATA135	0x4063061C	FULL	Memory buffer
SCB3_EZ_DATA136	0x40630620	FULL	Memory buffer
SCB3_EZ_DATA137	0x40630624	FULL	Memory buffer
SCB3_EZ_DATA138	0x40630628	FULL	Memory buffer
SCB3_EZ_DATA139	0x4063062C	FULL	Memory buffer
SCB3_EZ_DATA140	0x40630630	FULL	Memory buffer
SCB3_EZ_DATA141	0x40630634	FULL	Memory buffer
SCB3_EZ_DATA142	0x40630638	FULL	Memory buffer
SCB3_EZ_DATA143	0x4063063C	FULL	Memory buffer
SCB3_EZ_DATA144	0x40630640	FULL	Memory buffer
SCB3_EZ_DATA145	0x40630644	FULL	Memory buffer
SCB3_EZ_DATA146	0x40630648	FULL	Memory buffer
SCB3_EZ_DATA147	0x4063064C	FULL	Memory buffer
SCB3_EZ_DATA148	0x40630650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB3_EZ_DATA149	0x40630654	FULL	Memory buffer
SCB3_EZ_DATA150	0x40630658	FULL	Memory buffer
SCB3_EZ_DATA151	0x4063065C	FULL	Memory buffer
SCB3_EZ_DATA152	0x40630660	FULL	Memory buffer
SCB3_EZ_DATA153	0x40630664	FULL	Memory buffer
SCB3_EZ_DATA154	0x40630668	FULL	Memory buffer
SCB3_EZ_DATA155	0x4063066C	FULL	Memory buffer
SCB3_EZ_DATA156	0x40630670	FULL	Memory buffer
SCB3_EZ_DATA157	0x40630674	FULL	Memory buffer
SCB3_EZ_DATA158	0x40630678	FULL	Memory buffer
SCB3_EZ_DATA159	0x4063067C	FULL	Memory buffer
SCB3_EZ_DATA160	0x40630680	FULL	Memory buffer
SCB3_EZ_DATA161	0x40630684	FULL	Memory buffer
SCB3_EZ_DATA162	0x40630688	FULL	Memory buffer
SCB3_EZ_DATA163	0x4063068C	FULL	Memory buffer
SCB3_EZ_DATA164	0x40630690	FULL	Memory buffer
SCB3_EZ_DATA165	0x40630694	FULL	Memory buffer
SCB3_EZ_DATA166	0x40630698	FULL	Memory buffer
SCB3_EZ_DATA167	0x4063069C	FULL	Memory buffer
SCB3_EZ_DATA168	0x406306A0	FULL	Memory buffer
SCB3_EZ_DATA169	0x406306A4	FULL	Memory buffer
SCB3_EZ_DATA170	0x406306A8	FULL	Memory buffer
SCB3_EZ_DATA171	0x406306AC	FULL	Memory buffer
SCB3_EZ_DATA172	0x406306B0	FULL	Memory buffer
SCB3_EZ_DATA173	0x406306B4	FULL	Memory buffer
SCB3_EZ_DATA174	0x406306B8	FULL	Memory buffer
SCB3_EZ_DATA175	0x406306BC	FULL	Memory buffer
SCB3_EZ_DATA176	0x406306C0	FULL	Memory buffer
SCB3_EZ_DATA177	0x406306C4	FULL	Memory buffer
SCB3_EZ_DATA178	0x406306C8	FULL	Memory buffer
SCB3_EZ_DATA179	0x406306CC	FULL	Memory buffer
SCB3_EZ_DATA180	0x406306D0	FULL	Memory buffer
SCB3_EZ_DATA181	0x406306D4	FULL	Memory buffer
SCB3_EZ_DATA182	0x406306D8	FULL	Memory buffer
SCB3_EZ_DATA183	0x406306DC	FULL	Memory buffer
SCB3_EZ_DATA184	0x406306E0	FULL	Memory buffer
SCB3_EZ_DATA185	0x406306E4	FULL	Memory buffer
SCB3_EZ_DATA186	0x406306E8	FULL	Memory buffer
SCB3_EZ_DATA187	0x406306EC	FULL	Memory buffer
SCB3_EZ_DATA188	0x406306F0	FULL	Memory buffer
SCB3_EZ_DATA189	0x406306F4	FULL	Memory buffer
SCB3_EZ_DATA190	0x406306F8	FULL	Memory buffer
SCB3_EZ_DATA191	0x406306FC	FULL	Memory buffer
SCB3_EZ_DATA192	0x40630700	FULL	Memory buffer
SCB3_EZ_DATA193	0x40630704	FULL	Memory buffer
SCB3_EZ_DATA194	0x40630708	FULL	Memory buffer
SCB3_EZ_DATA195	0x4063070C	FULL	Memory buffer
SCB3_EZ_DATA196	0x40630710	FULL	Memory buffer
SCB3_EZ_DATA197	0x40630714	FULL	Memory buffer
SCB3_EZ_DATA198	0x40630718	FULL	Memory buffer
SCB3_EZ_DATA199	0x4063071C	FULL	Memory buffer
SCB3_EZ_DATA200	0x40630720	FULL	Memory buffer
SCB3_EZ_DATA201	0x40630724	FULL	Memory buffer
SCB3_EZ_DATA202	0x40630728	FULL	Memory buffer
SCB3_EZ_DATA203	0x4063072C	FULL	Memory buffer
SCB3_EZ_DATA204	0x40630730	FULL	Memory buffer
SCB3_EZ_DATA205	0x40630734	FULL	Memory buffer
SCB3_EZ_DATA206	0x40630738	FULL	Memory buffer
SCB3_EZ_DATA207	0x4063073C	FULL	Memory buffer
SCB3_EZ_DATA208	0x40630740	FULL	Memory buffer
SCB3_EZ_DATA209	0x40630744	FULL	Memory buffer
SCB3_EZ_DATA210	0x40630748	FULL	Memory buffer
SCB3_EZ_DATA211	0x4063074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB3_EZ_DATA212	0x40630750	FULL	Memory buffer
SCB3_EZ_DATA213	0x40630754	FULL	Memory buffer
SCB3_EZ_DATA214	0x40630758	FULL	Memory buffer
SCB3_EZ_DATA215	0x4063075C	FULL	Memory buffer
SCB3_EZ_DATA216	0x40630760	FULL	Memory buffer
SCB3_EZ_DATA217	0x40630764	FULL	Memory buffer
SCB3_EZ_DATA218	0x40630768	FULL	Memory buffer
SCB3_EZ_DATA219	0x4063076C	FULL	Memory buffer
SCB3_EZ_DATA220	0x40630770	FULL	Memory buffer
SCB3_EZ_DATA221	0x40630774	FULL	Memory buffer
SCB3_EZ_DATA222	0x40630778	FULL	Memory buffer
SCB3_EZ_DATA223	0x4063077C	FULL	Memory buffer
SCB3_EZ_DATA224	0x40630780	FULL	Memory buffer
SCB3_EZ_DATA225	0x40630784	FULL	Memory buffer
SCB3_EZ_DATA226	0x40630788	FULL	Memory buffer
SCB3_EZ_DATA227	0x4063078C	FULL	Memory buffer
SCB3_EZ_DATA228	0x40630790	FULL	Memory buffer
SCB3_EZ_DATA229	0x40630794	FULL	Memory buffer
SCB3_EZ_DATA230	0x40630798	FULL	Memory buffer
SCB3_EZ_DATA231	0x4063079C	FULL	Memory buffer
SCB3_EZ_DATA232	0x406307A0	FULL	Memory buffer
SCB3_EZ_DATA233	0x406307A4	FULL	Memory buffer
SCB3_EZ_DATA234	0x406307A8	FULL	Memory buffer
SCB3_EZ_DATA235	0x406307AC	FULL	Memory buffer
SCB3_EZ_DATA236	0x406307B0	FULL	Memory buffer
SCB3_EZ_DATA237	0x406307B4	FULL	Memory buffer
SCB3_EZ_DATA238	0x406307B8	FULL	Memory buffer
SCB3_EZ_DATA239	0x406307BC	FULL	Memory buffer
SCB3_EZ_DATA240	0x406307C0	FULL	Memory buffer
SCB3_EZ_DATA241	0x406307C4	FULL	Memory buffer
SCB3_EZ_DATA242	0x406307C8	FULL	Memory buffer
SCB3_EZ_DATA243	0x406307CC	FULL	Memory buffer
SCB3_EZ_DATA244	0x406307D0	FULL	Memory buffer
SCB3_EZ_DATA245	0x406307D4	FULL	Memory buffer
SCB3_EZ_DATA246	0x406307D8	FULL	Memory buffer
SCB3_EZ_DATA247	0x406307DC	FULL	Memory buffer
SCB3_EZ_DATA248	0x406307E0	FULL	Memory buffer
SCB3_EZ_DATA249	0x406307E4	FULL	Memory buffer
SCB3_EZ_DATA250	0x406307E8	FULL	Memory buffer
SCB3_EZ_DATA251	0x406307EC	FULL	Memory buffer
SCB3_EZ_DATA252	0x406307F0	FULL	Memory buffer
SCB3_EZ_DATA253	0x406307F4	FULL	Memory buffer
SCB3_EZ_DATA254	0x406307F8	FULL	Memory buffer
SCB3_EZ_DATA255	0x406307FC	FULL	Memory buffer
SCB3_INTR_CAUSE	0x40630E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB3_INTR_SPI_EC	0x40630EC0	FULL	Externally clocked SPI interrupt request
SCB3_INTR_SPI_EC_MASK	0x40630EC8	FULL	Externally clocked SPI interrupt mask
SCB3_INTR_SPI_EC_MASKED	0x40630ECC	FULL	Externally clocked SPI interrupt masked
SCB3_INTR_M	0x40630F00	FULL	Master interrupt request
SCB3_INTR_M_SET	0x40630F04	FULL	Master interrupt set request
SCB3_INTR_M_MASK	0x40630F08	FULL	Master interrupt mask
SCB3_INTR_M_MASKED	0x40630F0C	FULL	Master interrupt masked request
SCB3_INTR_S	0x40630F40	FULL	Slave interrupt request
SCB3_INTR_S_SET	0x40630F44	FULL	Slave interrupt set request
SCB3_INTR_S_MASK	0x40630F48	FULL	Slave interrupt mask
SCB3_INTR_S_MASKED	0x40630F4C	FULL	Slave interrupt masked request
SCB3_INTR_TX	0x40630F80	FULL	Transmitter interrupt request
SCB3_INTR_TX_SET	0x40630F84	FULL	Transmitter interrupt set request
SCB3_INTR_TX_MASK	0x40630F88	FULL	Transmitter interrupt mask
SCB3_INTR_TX_MASKED	0x40630F8C	FULL	Transmitter interrupt masked request
SCB3_INTR_RX	0x40630FC0	FULL	Receiver interrupt request
SCB3_INTR_RX_SET	0x40630FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB3_INTR_RX_MASK	0x40630FC8	FULL	Receiver interrupt mask
SCB3_INTR_RX_MASKED	0x40630FCC	FULL	Receiver interrupt masked request

24.5 SCB 4

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40640000

Size 0x10000

Slave Num MMIO6 - 4

Register Name	Address	Permission	Description
SCB4_CTRL	0x40640000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB4_STATUS	0x40640004	FULL	Generic status
SCB4_SPI_CTRL	0x40640020	FULL	SPI control
SCB4_SPI_STATUS	0x40640024	FULL	SPI status
SCB4_SPI_TX_CTRL	0x40640028	FULL	SPI transmitter control
SCB4_SPI_RX_CTRL	0x4064002C	FULL	SPI receiver control
SCB4_UART_CTRL	0x40640040	FULL	UART control
SCB4_UART_TX_CTRL	0x40640044	FULL	UART transmitter control
SCB4_UART_RX_CTRL	0x40640048	FULL	UART receiver control
SCB4_UART_RX_STATUS	0x4064004C	FULL	UART receiver status
SCB4_UART_FLOW_CTRL	0x40640050	FULL	UART flow control
SCB4_I2C_CTRL	0x40640060	FULL	I2C control
SCB4_I2C_STATUS	0x40640064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB4_I2C_M_CMD	0x40640068	FULL	I2C master command
SCB4_I2C_S_CMD	0x4064006C	FULL	I2C slave command
SCB4_I2C_CFG	0x40640070	FULL	I2C configuration
SCB4_TX_CTRL	0x40640200	FULL	Transmitter control
SCB4_TX_FIFO_CTRL	0x40640204	FULL	Transmitter FIFO control
SCB4_TX_FIFO_STATUS	0x40640208	FULL	Transmitter FIFO status
SCB4_TX_FIFO_WR	0x40640240	FULL	Transmitter FIFO write
SCB4_RX_CTRL	0x40640300	FULL	Receiver control
SCB4_RX_FIFO_CTRL	0x40640304	FULL	Receiver FIFO control
SCB4_RX_FIFO_STATUS	0x40640308	FULL	Receiver FIFO status
SCB4_RX_MATCH	0x40640310	FULL	Slave address and mask
SCB4_RX_FIFO_RD	0x40640340	FULL	Receiver FIFO read
SCB4_RX_FIFO_RD_SILENT	0x40640344	FULL	Receiver FIFO read silent
SCB4_EZ_DATA0	0x40640400	FULL	Memory buffer
SCB4_EZ_DATA1	0x40640404	FULL	Memory buffer
SCB4_EZ_DATA2	0x40640408	FULL	Memory buffer
SCB4_EZ_DATA3	0x4064040C	FULL	Memory buffer
SCB4_EZ_DATA4	0x40640410	FULL	Memory buffer
SCB4_EZ_DATA5	0x40640414	FULL	Memory buffer
SCB4_EZ_DATA6	0x40640418	FULL	Memory buffer
SCB4_EZ_DATA7	0x4064041C	FULL	Memory buffer
SCB4_EZ_DATA8	0x40640420	FULL	Memory buffer
SCB4_EZ_DATA9	0x40640424	FULL	Memory buffer
SCB4_EZ_DATA10	0x40640428	FULL	Memory buffer
SCB4_EZ_DATA11	0x4064042C	FULL	Memory buffer
SCB4_EZ_DATA12	0x40640430	FULL	Memory buffer
SCB4_EZ_DATA13	0x40640434	FULL	Memory buffer
SCB4_EZ_DATA14	0x40640438	FULL	Memory buffer
SCB4_EZ_DATA15	0x4064043C	FULL	Memory buffer
SCB4_EZ_DATA16	0x40640440	FULL	Memory buffer
SCB4_EZ_DATA17	0x40640444	FULL	Memory buffer
SCB4_EZ_DATA18	0x40640448	FULL	Memory buffer
SCB4_EZ_DATA19	0x4064044C	FULL	Memory buffer
SCB4_EZ_DATA20	0x40640450	FULL	Memory buffer
SCB4_EZ_DATA21	0x40640454	FULL	Memory buffer
SCB4_EZ_DATA22	0x40640458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB4_EZ_DATA23	0x4064045C	FULL	Memory buffer
SCB4_EZ_DATA24	0x40640460	FULL	Memory buffer
SCB4_EZ_DATA25	0x40640464	FULL	Memory buffer
SCB4_EZ_DATA26	0x40640468	FULL	Memory buffer
SCB4_EZ_DATA27	0x4064046C	FULL	Memory buffer
SCB4_EZ_DATA28	0x40640470	FULL	Memory buffer
SCB4_EZ_DATA29	0x40640474	FULL	Memory buffer
SCB4_EZ_DATA30	0x40640478	FULL	Memory buffer
SCB4_EZ_DATA31	0x4064047C	FULL	Memory buffer
SCB4_EZ_DATA32	0x40640480	FULL	Memory buffer
SCB4_EZ_DATA33	0x40640484	FULL	Memory buffer
SCB4_EZ_DATA34	0x40640488	FULL	Memory buffer
SCB4_EZ_DATA35	0x4064048C	FULL	Memory buffer
SCB4_EZ_DATA36	0x40640490	FULL	Memory buffer
SCB4_EZ_DATA37	0x40640494	FULL	Memory buffer
SCB4_EZ_DATA38	0x40640498	FULL	Memory buffer
SCB4_EZ_DATA39	0x4064049C	FULL	Memory buffer
SCB4_EZ_DATA40	0x406404A0	FULL	Memory buffer
SCB4_EZ_DATA41	0x406404A4	FULL	Memory buffer
SCB4_EZ_DATA42	0x406404A8	FULL	Memory buffer
SCB4_EZ_DATA43	0x406404AC	FULL	Memory buffer
SCB4_EZ_DATA44	0x406404B0	FULL	Memory buffer
SCB4_EZ_DATA45	0x406404B4	FULL	Memory buffer
SCB4_EZ_DATA46	0x406404B8	FULL	Memory buffer
SCB4_EZ_DATA47	0x406404BC	FULL	Memory buffer
SCB4_EZ_DATA48	0x406404C0	FULL	Memory buffer
SCB4_EZ_DATA49	0x406404C4	FULL	Memory buffer
SCB4_EZ_DATA50	0x406404C8	FULL	Memory buffer
SCB4_EZ_DATA51	0x406404CC	FULL	Memory buffer
SCB4_EZ_DATA52	0x406404D0	FULL	Memory buffer
SCB4_EZ_DATA53	0x406404D4	FULL	Memory buffer
SCB4_EZ_DATA54	0x406404D8	FULL	Memory buffer
SCB4_EZ_DATA55	0x406404DC	FULL	Memory buffer
SCB4_EZ_DATA56	0x406404E0	FULL	Memory buffer
SCB4_EZ_DATA57	0x406404E4	FULL	Memory buffer
SCB4_EZ_DATA58	0x406404E8	FULL	Memory buffer
SCB4_EZ_DATA59	0x406404EC	FULL	Memory buffer
SCB4_EZ_DATA60	0x406404F0	FULL	Memory buffer
SCB4_EZ_DATA61	0x406404F4	FULL	Memory buffer
SCB4_EZ_DATA62	0x406404F8	FULL	Memory buffer
SCB4_EZ_DATA63	0x406404FC	FULL	Memory buffer
SCB4_EZ_DATA64	0x40640500	FULL	Memory buffer
SCB4_EZ_DATA65	0x40640504	FULL	Memory buffer
SCB4_EZ_DATA66	0x40640508	FULL	Memory buffer
SCB4_EZ_DATA67	0x4064050C	FULL	Memory buffer
SCB4_EZ_DATA68	0x40640510	FULL	Memory buffer
SCB4_EZ_DATA69	0x40640514	FULL	Memory buffer
SCB4_EZ_DATA70	0x40640518	FULL	Memory buffer
SCB4_EZ_DATA71	0x4064051C	FULL	Memory buffer
SCB4_EZ_DATA72	0x40640520	FULL	Memory buffer
SCB4_EZ_DATA73	0x40640524	FULL	Memory buffer
SCB4_EZ_DATA74	0x40640528	FULL	Memory buffer
SCB4_EZ_DATA75	0x4064052C	FULL	Memory buffer
SCB4_EZ_DATA76	0x40640530	FULL	Memory buffer
SCB4_EZ_DATA77	0x40640534	FULL	Memory buffer
SCB4_EZ_DATA78	0x40640538	FULL	Memory buffer
SCB4_EZ_DATA79	0x4064053C	FULL	Memory buffer
SCB4_EZ_DATA80	0x40640540	FULL	Memory buffer
SCB4_EZ_DATA81	0x40640544	FULL	Memory buffer
SCB4_EZ_DATA82	0x40640548	FULL	Memory buffer
SCB4_EZ_DATA83	0x4064054C	FULL	Memory buffer
SCB4_EZ_DATA84	0x40640550	FULL	Memory buffer
SCB4_EZ_DATA85	0x40640554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB4_EZ_DATA86	0x40640558	FULL	Memory buffer
SCB4_EZ_DATA87	0x4064055C	FULL	Memory buffer
SCB4_EZ_DATA88	0x40640560	FULL	Memory buffer
SCB4_EZ_DATA89	0x40640564	FULL	Memory buffer
SCB4_EZ_DATA90	0x40640568	FULL	Memory buffer
SCB4_EZ_DATA91	0x4064056C	FULL	Memory buffer
SCB4_EZ_DATA92	0x40640570	FULL	Memory buffer
SCB4_EZ_DATA93	0x40640574	FULL	Memory buffer
SCB4_EZ_DATA94	0x40640578	FULL	Memory buffer
SCB4_EZ_DATA95	0x4064057C	FULL	Memory buffer
SCB4_EZ_DATA96	0x40640580	FULL	Memory buffer
SCB4_EZ_DATA97	0x40640584	FULL	Memory buffer
SCB4_EZ_DATA98	0x40640588	FULL	Memory buffer
SCB4_EZ_DATA99	0x4064058C	FULL	Memory buffer
SCB4_EZ_DATA100	0x40640590	FULL	Memory buffer
SCB4_EZ_DATA101	0x40640594	FULL	Memory buffer
SCB4_EZ_DATA102	0x40640598	FULL	Memory buffer
SCB4_EZ_DATA103	0x4064059C	FULL	Memory buffer
SCB4_EZ_DATA104	0x406405A0	FULL	Memory buffer
SCB4_EZ_DATA105	0x406405A4	FULL	Memory buffer
SCB4_EZ_DATA106	0x406405A8	FULL	Memory buffer
SCB4_EZ_DATA107	0x406405AC	FULL	Memory buffer
SCB4_EZ_DATA108	0x406405B0	FULL	Memory buffer
SCB4_EZ_DATA109	0x406405B4	FULL	Memory buffer
SCB4_EZ_DATA110	0x406405B8	FULL	Memory buffer
SCB4_EZ_DATA111	0x406405BC	FULL	Memory buffer
SCB4_EZ_DATA112	0x406405C0	FULL	Memory buffer
SCB4_EZ_DATA113	0x406405C4	FULL	Memory buffer
SCB4_EZ_DATA114	0x406405C8	FULL	Memory buffer
SCB4_EZ_DATA115	0x406405CC	FULL	Memory buffer
SCB4_EZ_DATA116	0x406405D0	FULL	Memory buffer
SCB4_EZ_DATA117	0x406405D4	FULL	Memory buffer
SCB4_EZ_DATA118	0x406405D8	FULL	Memory buffer
SCB4_EZ_DATA119	0x406405DC	FULL	Memory buffer
SCB4_EZ_DATA120	0x406405E0	FULL	Memory buffer
SCB4_EZ_DATA121	0x406405E4	FULL	Memory buffer
SCB4_EZ_DATA122	0x406405E8	FULL	Memory buffer
SCB4_EZ_DATA123	0x406405EC	FULL	Memory buffer
SCB4_EZ_DATA124	0x406405F0	FULL	Memory buffer
SCB4_EZ_DATA125	0x406405F4	FULL	Memory buffer
SCB4_EZ_DATA126	0x406405F8	FULL	Memory buffer
SCB4_EZ_DATA127	0x406405FC	FULL	Memory buffer
SCB4_EZ_DATA128	0x40640600	FULL	Memory buffer
SCB4_EZ_DATA129	0x40640604	FULL	Memory buffer
SCB4_EZ_DATA130	0x40640608	FULL	Memory buffer
SCB4_EZ_DATA131	0x4064060C	FULL	Memory buffer
SCB4_EZ_DATA132	0x40640610	FULL	Memory buffer
SCB4_EZ_DATA133	0x40640614	FULL	Memory buffer
SCB4_EZ_DATA134	0x40640618	FULL	Memory buffer
SCB4_EZ_DATA135	0x4064061C	FULL	Memory buffer
SCB4_EZ_DATA136	0x40640620	FULL	Memory buffer
SCB4_EZ_DATA137	0x40640624	FULL	Memory buffer
SCB4_EZ_DATA138	0x40640628	FULL	Memory buffer
SCB4_EZ_DATA139	0x4064062C	FULL	Memory buffer
SCB4_EZ_DATA140	0x40640630	FULL	Memory buffer
SCB4_EZ_DATA141	0x40640634	FULL	Memory buffer
SCB4_EZ_DATA142	0x40640638	FULL	Memory buffer
SCB4_EZ_DATA143	0x4064063C	FULL	Memory buffer
SCB4_EZ_DATA144	0x40640640	FULL	Memory buffer
SCB4_EZ_DATA145	0x40640644	FULL	Memory buffer
SCB4_EZ_DATA146	0x40640648	FULL	Memory buffer
SCB4_EZ_DATA147	0x4064064C	FULL	Memory buffer
SCB4_EZ_DATA148	0x40640650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB4_EZ_DATA149	0x40640654	FULL	Memory buffer
SCB4_EZ_DATA150	0x40640658	FULL	Memory buffer
SCB4_EZ_DATA151	0x4064065C	FULL	Memory buffer
SCB4_EZ_DATA152	0x40640660	FULL	Memory buffer
SCB4_EZ_DATA153	0x40640664	FULL	Memory buffer
SCB4_EZ_DATA154	0x40640668	FULL	Memory buffer
SCB4_EZ_DATA155	0x4064066C	FULL	Memory buffer
SCB4_EZ_DATA156	0x40640670	FULL	Memory buffer
SCB4_EZ_DATA157	0x40640674	FULL	Memory buffer
SCB4_EZ_DATA158	0x40640678	FULL	Memory buffer
SCB4_EZ_DATA159	0x4064067C	FULL	Memory buffer
SCB4_EZ_DATA160	0x40640680	FULL	Memory buffer
SCB4_EZ_DATA161	0x40640684	FULL	Memory buffer
SCB4_EZ_DATA162	0x40640688	FULL	Memory buffer
SCB4_EZ_DATA163	0x4064068C	FULL	Memory buffer
SCB4_EZ_DATA164	0x40640690	FULL	Memory buffer
SCB4_EZ_DATA165	0x40640694	FULL	Memory buffer
SCB4_EZ_DATA166	0x40640698	FULL	Memory buffer
SCB4_EZ_DATA167	0x4064069C	FULL	Memory buffer
SCB4_EZ_DATA168	0x406406A0	FULL	Memory buffer
SCB4_EZ_DATA169	0x406406A4	FULL	Memory buffer
SCB4_EZ_DATA170	0x406406A8	FULL	Memory buffer
SCB4_EZ_DATA171	0x406406AC	FULL	Memory buffer
SCB4_EZ_DATA172	0x406406B0	FULL	Memory buffer
SCB4_EZ_DATA173	0x406406B4	FULL	Memory buffer
SCB4_EZ_DATA174	0x406406B8	FULL	Memory buffer
SCB4_EZ_DATA175	0x406406BC	FULL	Memory buffer
SCB4_EZ_DATA176	0x406406C0	FULL	Memory buffer
SCB4_EZ_DATA177	0x406406C4	FULL	Memory buffer
SCB4_EZ_DATA178	0x406406C8	FULL	Memory buffer
SCB4_EZ_DATA179	0x406406CC	FULL	Memory buffer
SCB4_EZ_DATA180	0x406406D0	FULL	Memory buffer
SCB4_EZ_DATA181	0x406406D4	FULL	Memory buffer
SCB4_EZ_DATA182	0x406406D8	FULL	Memory buffer
SCB4_EZ_DATA183	0x406406DC	FULL	Memory buffer
SCB4_EZ_DATA184	0x406406E0	FULL	Memory buffer
SCB4_EZ_DATA185	0x406406E4	FULL	Memory buffer
SCB4_EZ_DATA186	0x406406E8	FULL	Memory buffer
SCB4_EZ_DATA187	0x406406EC	FULL	Memory buffer
SCB4_EZ_DATA188	0x406406F0	FULL	Memory buffer
SCB4_EZ_DATA189	0x406406F4	FULL	Memory buffer
SCB4_EZ_DATA190	0x406406F8	FULL	Memory buffer
SCB4_EZ_DATA191	0x406406FC	FULL	Memory buffer
SCB4_EZ_DATA192	0x40640700	FULL	Memory buffer
SCB4_EZ_DATA193	0x40640704	FULL	Memory buffer
SCB4_EZ_DATA194	0x40640708	FULL	Memory buffer
SCB4_EZ_DATA195	0x4064070C	FULL	Memory buffer
SCB4_EZ_DATA196	0x40640710	FULL	Memory buffer
SCB4_EZ_DATA197	0x40640714	FULL	Memory buffer
SCB4_EZ_DATA198	0x40640718	FULL	Memory buffer
SCB4_EZ_DATA199	0x4064071C	FULL	Memory buffer
SCB4_EZ_DATA200	0x40640720	FULL	Memory buffer
SCB4_EZ_DATA201	0x40640724	FULL	Memory buffer
SCB4_EZ_DATA202	0x40640728	FULL	Memory buffer
SCB4_EZ_DATA203	0x4064072C	FULL	Memory buffer
SCB4_EZ_DATA204	0x40640730	FULL	Memory buffer
SCB4_EZ_DATA205	0x40640734	FULL	Memory buffer
SCB4_EZ_DATA206	0x40640738	FULL	Memory buffer
SCB4_EZ_DATA207	0x4064073C	FULL	Memory buffer
SCB4_EZ_DATA208	0x40640740	FULL	Memory buffer
SCB4_EZ_DATA209	0x40640744	FULL	Memory buffer
SCB4_EZ_DATA210	0x40640748	FULL	Memory buffer
SCB4_EZ_DATA211	0x4064074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB4_EZ_DATA212	0x40640750	FULL	Memory buffer
SCB4_EZ_DATA213	0x40640754	FULL	Memory buffer
SCB4_EZ_DATA214	0x40640758	FULL	Memory buffer
SCB4_EZ_DATA215	0x4064075C	FULL	Memory buffer
SCB4_EZ_DATA216	0x40640760	FULL	Memory buffer
SCB4_EZ_DATA217	0x40640764	FULL	Memory buffer
SCB4_EZ_DATA218	0x40640768	FULL	Memory buffer
SCB4_EZ_DATA219	0x4064076C	FULL	Memory buffer
SCB4_EZ_DATA220	0x40640770	FULL	Memory buffer
SCB4_EZ_DATA221	0x40640774	FULL	Memory buffer
SCB4_EZ_DATA222	0x40640778	FULL	Memory buffer
SCB4_EZ_DATA223	0x4064077C	FULL	Memory buffer
SCB4_EZ_DATA224	0x40640780	FULL	Memory buffer
SCB4_EZ_DATA225	0x40640784	FULL	Memory buffer
SCB4_EZ_DATA226	0x40640788	FULL	Memory buffer
SCB4_EZ_DATA227	0x4064078C	FULL	Memory buffer
SCB4_EZ_DATA228	0x40640790	FULL	Memory buffer
SCB4_EZ_DATA229	0x40640794	FULL	Memory buffer
SCB4_EZ_DATA230	0x40640798	FULL	Memory buffer
SCB4_EZ_DATA231	0x4064079C	FULL	Memory buffer
SCB4_EZ_DATA232	0x406407A0	FULL	Memory buffer
SCB4_EZ_DATA233	0x406407A4	FULL	Memory buffer
SCB4_EZ_DATA234	0x406407A8	FULL	Memory buffer
SCB4_EZ_DATA235	0x406407AC	FULL	Memory buffer
SCB4_EZ_DATA236	0x406407B0	FULL	Memory buffer
SCB4_EZ_DATA237	0x406407B4	FULL	Memory buffer
SCB4_EZ_DATA238	0x406407B8	FULL	Memory buffer
SCB4_EZ_DATA239	0x406407BC	FULL	Memory buffer
SCB4_EZ_DATA240	0x406407C0	FULL	Memory buffer
SCB4_EZ_DATA241	0x406407C4	FULL	Memory buffer
SCB4_EZ_DATA242	0x406407C8	FULL	Memory buffer
SCB4_EZ_DATA243	0x406407CC	FULL	Memory buffer
SCB4_EZ_DATA244	0x406407D0	FULL	Memory buffer
SCB4_EZ_DATA245	0x406407D4	FULL	Memory buffer
SCB4_EZ_DATA246	0x406407D8	FULL	Memory buffer
SCB4_EZ_DATA247	0x406407DC	FULL	Memory buffer
SCB4_EZ_DATA248	0x406407E0	FULL	Memory buffer
SCB4_EZ_DATA249	0x406407E4	FULL	Memory buffer
SCB4_EZ_DATA250	0x406407E8	FULL	Memory buffer
SCB4_EZ_DATA251	0x406407EC	FULL	Memory buffer
SCB4_EZ_DATA252	0x406407F0	FULL	Memory buffer
SCB4_EZ_DATA253	0x406407F4	FULL	Memory buffer
SCB4_EZ_DATA254	0x406407F8	FULL	Memory buffer
SCB4_EZ_DATA255	0x406407FC	FULL	Memory buffer
SCB4_INTR_CAUSE	0x40640E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB4_INTR_SPI_EC	0x40640EC0	FULL	Externally clocked SPI interrupt request
SCB4_INTR_SPI_EC_MASK	0x40640EC8	FULL	Externally clocked SPI interrupt mask
SCB4_INTR_SPI_EC_MASKED	0x40640ECC	FULL	Externally clocked SPI interrupt masked
SCB4_INTR_M	0x40640F00	FULL	Master interrupt request
SCB4_INTR_M_SET	0x40640F04	FULL	Master interrupt set request
SCB4_INTR_M_MASK	0x40640F08	FULL	Master interrupt mask
SCB4_INTR_M_MASKED	0x40640F0C	FULL	Master interrupt masked request
SCB4_INTR_S	0x40640F40	FULL	Slave interrupt request
SCB4_INTR_S_SET	0x40640F44	FULL	Slave interrupt set request
SCB4_INTR_S_MASK	0x40640F48	FULL	Slave interrupt mask
SCB4_INTR_S_MASKED	0x40640F4C	FULL	Slave interrupt masked request
SCB4_INTR_TX	0x40640F80	FULL	Transmitter interrupt request
SCB4_INTR_TX_SET	0x40640F84	FULL	Transmitter interrupt set request
SCB4_INTR_TX_MASK	0x40640F88	FULL	Transmitter interrupt mask
SCB4_INTR_TX_MASKED	0x40640F8C	FULL	Transmitter interrupt masked request
SCB4_INTR_RX	0x40640FC0	FULL	Receiver interrupt request
SCB4_INTR_RX_SET	0x40640FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB4_INTR_RX_MASK	0x40640FC8	FULL	Receiver interrupt mask
SCB4_INTR_RX_MASKED	0x40640FCC	FULL	Receiver interrupt masked request

24.6 SCB 5

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40650000

Size 0x10000

Slave Num MMIO6 - 5

Register Name	Address	Permission	Description
SCB5_CTRL	0x40650000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB5_STATUS	0x40650004	FULL	Generic status
SCB5_SPI_CTRL	0x40650020	FULL	SPI control
SCB5_SPI_STATUS	0x40650024	FULL	SPI status
SCB5_SPI_TX_CTRL	0x40650028	FULL	SPI transmitter control
SCB5_SPI_RX_CTRL	0x4065002C	FULL	SPI receiver control
SCB5_UART_CTRL	0x40650040	FULL	UART control
SCB5_UART_TX_CTRL	0x40650044	FULL	UART transmitter control
SCB5_UART_RX_CTRL	0x40650048	FULL	UART receiver control
SCB5_UART_RX_STATUS	0x4065004C	FULL	UART receiver status
SCB5_UART_FLOW_CTRL	0x40650050	FULL	UART flow control
SCB5_I2C_CTRL	0x40650060	FULL	I2C control
SCB5_I2C_STATUS	0x40650064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB5_I2C_M_CMD	0x40650068	FULL	I2C master command
SCB5_I2C_S_CMD	0x4065006C	FULL	I2C slave command
SCB5_I2C_CFG	0x40650070	FULL	I2C configuration
SCB5_TX_CTRL	0x40650200	FULL	Transmitter control
SCB5_TX_FIFO_CTRL	0x40650204	FULL	Transmitter FIFO control
SCB5_TX_FIFO_STATUS	0x40650208	FULL	Transmitter FIFO status
SCB5_TX_FIFO_WR	0x40650240	FULL	Transmitter FIFO write
SCB5_RX_CTRL	0x40650300	FULL	Receiver control
SCB5_RX_FIFO_CTRL	0x40650304	FULL	Receiver FIFO control
SCB5_RX_FIFO_STATUS	0x40650308	FULL	Receiver FIFO status
SCB5_RX_MATCH	0x40650310	FULL	Slave address and mask
SCB5_RX_FIFO_RD	0x40650340	FULL	Receiver FIFO read
SCB5_RX_FIFO_RD_SILENT	0x40650344	FULL	Receiver FIFO read silent
SCB5_EZ_DATA0	0x40650400	FULL	Memory buffer
SCB5_EZ_DATA1	0x40650404	FULL	Memory buffer
SCB5_EZ_DATA2	0x40650408	FULL	Memory buffer
SCB5_EZ_DATA3	0x4065040C	FULL	Memory buffer
SCB5_EZ_DATA4	0x40650410	FULL	Memory buffer
SCB5_EZ_DATA5	0x40650414	FULL	Memory buffer
SCB5_EZ_DATA6	0x40650418	FULL	Memory buffer
SCB5_EZ_DATA7	0x4065041C	FULL	Memory buffer
SCB5_EZ_DATA8	0x40650420	FULL	Memory buffer
SCB5_EZ_DATA9	0x40650424	FULL	Memory buffer
SCB5_EZ_DATA10	0x40650428	FULL	Memory buffer
SCB5_EZ_DATA11	0x4065042C	FULL	Memory buffer
SCB5_EZ_DATA12	0x40650430	FULL	Memory buffer
SCB5_EZ_DATA13	0x40650434	FULL	Memory buffer
SCB5_EZ_DATA14	0x40650438	FULL	Memory buffer
SCB5_EZ_DATA15	0x4065043C	FULL	Memory buffer
SCB5_EZ_DATA16	0x40650440	FULL	Memory buffer
SCB5_EZ_DATA17	0x40650444	FULL	Memory buffer
SCB5_EZ_DATA18	0x40650448	FULL	Memory buffer
SCB5_EZ_DATA19	0x4065044C	FULL	Memory buffer
SCB5_EZ_DATA20	0x40650450	FULL	Memory buffer
SCB5_EZ_DATA21	0x40650454	FULL	Memory buffer
SCB5_EZ_DATA22	0x40650458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB5_EZ_DATA23	0x4065045C	FULL	Memory buffer
SCB5_EZ_DATA24	0x40650460	FULL	Memory buffer
SCB5_EZ_DATA25	0x40650464	FULL	Memory buffer
SCB5_EZ_DATA26	0x40650468	FULL	Memory buffer
SCB5_EZ_DATA27	0x4065046C	FULL	Memory buffer
SCB5_EZ_DATA28	0x40650470	FULL	Memory buffer
SCB5_EZ_DATA29	0x40650474	FULL	Memory buffer
SCB5_EZ_DATA30	0x40650478	FULL	Memory buffer
SCB5_EZ_DATA31	0x4065047C	FULL	Memory buffer
SCB5_EZ_DATA32	0x40650480	FULL	Memory buffer
SCB5_EZ_DATA33	0x40650484	FULL	Memory buffer
SCB5_EZ_DATA34	0x40650488	FULL	Memory buffer
SCB5_EZ_DATA35	0x4065048C	FULL	Memory buffer
SCB5_EZ_DATA36	0x40650490	FULL	Memory buffer
SCB5_EZ_DATA37	0x40650494	FULL	Memory buffer
SCB5_EZ_DATA38	0x40650498	FULL	Memory buffer
SCB5_EZ_DATA39	0x4065049C	FULL	Memory buffer
SCB5_EZ_DATA40	0x406504A0	FULL	Memory buffer
SCB5_EZ_DATA41	0x406504A4	FULL	Memory buffer
SCB5_EZ_DATA42	0x406504A8	FULL	Memory buffer
SCB5_EZ_DATA43	0x406504AC	FULL	Memory buffer
SCB5_EZ_DATA44	0x406504B0	FULL	Memory buffer
SCB5_EZ_DATA45	0x406504B4	FULL	Memory buffer
SCB5_EZ_DATA46	0x406504B8	FULL	Memory buffer
SCB5_EZ_DATA47	0x406504BC	FULL	Memory buffer
SCB5_EZ_DATA48	0x406504C0	FULL	Memory buffer
SCB5_EZ_DATA49	0x406504C4	FULL	Memory buffer
SCB5_EZ_DATA50	0x406504C8	FULL	Memory buffer
SCB5_EZ_DATA51	0x406504CC	FULL	Memory buffer
SCB5_EZ_DATA52	0x406504D0	FULL	Memory buffer
SCB5_EZ_DATA53	0x406504D4	FULL	Memory buffer
SCB5_EZ_DATA54	0x406504D8	FULL	Memory buffer
SCB5_EZ_DATA55	0x406504DC	FULL	Memory buffer
SCB5_EZ_DATA56	0x406504E0	FULL	Memory buffer
SCB5_EZ_DATA57	0x406504E4	FULL	Memory buffer
SCB5_EZ_DATA58	0x406504E8	FULL	Memory buffer
SCB5_EZ_DATA59	0x406504EC	FULL	Memory buffer
SCB5_EZ_DATA60	0x406504F0	FULL	Memory buffer
SCB5_EZ_DATA61	0x406504F4	FULL	Memory buffer
SCB5_EZ_DATA62	0x406504F8	FULL	Memory buffer
SCB5_EZ_DATA63	0x406504FC	FULL	Memory buffer
SCB5_EZ_DATA64	0x40650500	FULL	Memory buffer
SCB5_EZ_DATA65	0x40650504	FULL	Memory buffer
SCB5_EZ_DATA66	0x40650508	FULL	Memory buffer
SCB5_EZ_DATA67	0x4065050C	FULL	Memory buffer
SCB5_EZ_DATA68	0x40650510	FULL	Memory buffer
SCB5_EZ_DATA69	0x40650514	FULL	Memory buffer
SCB5_EZ_DATA70	0x40650518	FULL	Memory buffer
SCB5_EZ_DATA71	0x4065051C	FULL	Memory buffer
SCB5_EZ_DATA72	0x40650520	FULL	Memory buffer
SCB5_EZ_DATA73	0x40650524	FULL	Memory buffer
SCB5_EZ_DATA74	0x40650528	FULL	Memory buffer
SCB5_EZ_DATA75	0x4065052C	FULL	Memory buffer
SCB5_EZ_DATA76	0x40650530	FULL	Memory buffer
SCB5_EZ_DATA77	0x40650534	FULL	Memory buffer
SCB5_EZ_DATA78	0x40650538	FULL	Memory buffer
SCB5_EZ_DATA79	0x4065053C	FULL	Memory buffer
SCB5_EZ_DATA80	0x40650540	FULL	Memory buffer
SCB5_EZ_DATA81	0x40650544	FULL	Memory buffer
SCB5_EZ_DATA82	0x40650548	FULL	Memory buffer
SCB5_EZ_DATA83	0x4065054C	FULL	Memory buffer
SCB5_EZ_DATA84	0x40650550	FULL	Memory buffer
SCB5_EZ_DATA85	0x40650554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB5_EZ_DATA86	0x40650558	FULL	Memory buffer
SCB5_EZ_DATA87	0x4065055C	FULL	Memory buffer
SCB5_EZ_DATA88	0x40650560	FULL	Memory buffer
SCB5_EZ_DATA89	0x40650564	FULL	Memory buffer
SCB5_EZ_DATA90	0x40650568	FULL	Memory buffer
SCB5_EZ_DATA91	0x4065056C	FULL	Memory buffer
SCB5_EZ_DATA92	0x40650570	FULL	Memory buffer
SCB5_EZ_DATA93	0x40650574	FULL	Memory buffer
SCB5_EZ_DATA94	0x40650578	FULL	Memory buffer
SCB5_EZ_DATA95	0x4065057C	FULL	Memory buffer
SCB5_EZ_DATA96	0x40650580	FULL	Memory buffer
SCB5_EZ_DATA97	0x40650584	FULL	Memory buffer
SCB5_EZ_DATA98	0x40650588	FULL	Memory buffer
SCB5_EZ_DATA99	0x4065058C	FULL	Memory buffer
SCB5_EZ_DATA100	0x40650590	FULL	Memory buffer
SCB5_EZ_DATA101	0x40650594	FULL	Memory buffer
SCB5_EZ_DATA102	0x40650598	FULL	Memory buffer
SCB5_EZ_DATA103	0x4065059C	FULL	Memory buffer
SCB5_EZ_DATA104	0x406505A0	FULL	Memory buffer
SCB5_EZ_DATA105	0x406505A4	FULL	Memory buffer
SCB5_EZ_DATA106	0x406505A8	FULL	Memory buffer
SCB5_EZ_DATA107	0x406505AC	FULL	Memory buffer
SCB5_EZ_DATA108	0x406505B0	FULL	Memory buffer
SCB5_EZ_DATA109	0x406505B4	FULL	Memory buffer
SCB5_EZ_DATA110	0x406505B8	FULL	Memory buffer
SCB5_EZ_DATA111	0x406505BC	FULL	Memory buffer
SCB5_EZ_DATA112	0x406505C0	FULL	Memory buffer
SCB5_EZ_DATA113	0x406505C4	FULL	Memory buffer
SCB5_EZ_DATA114	0x406505C8	FULL	Memory buffer
SCB5_EZ_DATA115	0x406505CC	FULL	Memory buffer
SCB5_EZ_DATA116	0x406505D0	FULL	Memory buffer
SCB5_EZ_DATA117	0x406505D4	FULL	Memory buffer
SCB5_EZ_DATA118	0x406505D8	FULL	Memory buffer
SCB5_EZ_DATA119	0x406505DC	FULL	Memory buffer
SCB5_EZ_DATA120	0x406505E0	FULL	Memory buffer
SCB5_EZ_DATA121	0x406505E4	FULL	Memory buffer
SCB5_EZ_DATA122	0x406505E8	FULL	Memory buffer
SCB5_EZ_DATA123	0x406505EC	FULL	Memory buffer
SCB5_EZ_DATA124	0x406505F0	FULL	Memory buffer
SCB5_EZ_DATA125	0x406505F4	FULL	Memory buffer
SCB5_EZ_DATA126	0x406505F8	FULL	Memory buffer
SCB5_EZ_DATA127	0x406505FC	FULL	Memory buffer
SCB5_EZ_DATA128	0x40650600	FULL	Memory buffer
SCB5_EZ_DATA129	0x40650604	FULL	Memory buffer
SCB5_EZ_DATA130	0x40650608	FULL	Memory buffer
SCB5_EZ_DATA131	0x4065060C	FULL	Memory buffer
SCB5_EZ_DATA132	0x40650610	FULL	Memory buffer
SCB5_EZ_DATA133	0x40650614	FULL	Memory buffer
SCB5_EZ_DATA134	0x40650618	FULL	Memory buffer
SCB5_EZ_DATA135	0x4065061C	FULL	Memory buffer
SCB5_EZ_DATA136	0x40650620	FULL	Memory buffer
SCB5_EZ_DATA137	0x40650624	FULL	Memory buffer
SCB5_EZ_DATA138	0x40650628	FULL	Memory buffer
SCB5_EZ_DATA139	0x4065062C	FULL	Memory buffer
SCB5_EZ_DATA140	0x40650630	FULL	Memory buffer
SCB5_EZ_DATA141	0x40650634	FULL	Memory buffer
SCB5_EZ_DATA142	0x40650638	FULL	Memory buffer
SCB5_EZ_DATA143	0x4065063C	FULL	Memory buffer
SCB5_EZ_DATA144	0x40650640	FULL	Memory buffer
SCB5_EZ_DATA145	0x40650644	FULL	Memory buffer
SCB5_EZ_DATA146	0x40650648	FULL	Memory buffer
SCB5_EZ_DATA147	0x4065064C	FULL	Memory buffer
SCB5_EZ_DATA148	0x40650650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB5_EZ_DATA149	0x40650654	FULL	Memory buffer
SCB5_EZ_DATA150	0x40650658	FULL	Memory buffer
SCB5_EZ_DATA151	0x4065065C	FULL	Memory buffer
SCB5_EZ_DATA152	0x40650660	FULL	Memory buffer
SCB5_EZ_DATA153	0x40650664	FULL	Memory buffer
SCB5_EZ_DATA154	0x40650668	FULL	Memory buffer
SCB5_EZ_DATA155	0x4065066C	FULL	Memory buffer
SCB5_EZ_DATA156	0x40650670	FULL	Memory buffer
SCB5_EZ_DATA157	0x40650674	FULL	Memory buffer
SCB5_EZ_DATA158	0x40650678	FULL	Memory buffer
SCB5_EZ_DATA159	0x4065067C	FULL	Memory buffer
SCB5_EZ_DATA160	0x40650680	FULL	Memory buffer
SCB5_EZ_DATA161	0x40650684	FULL	Memory buffer
SCB5_EZ_DATA162	0x40650688	FULL	Memory buffer
SCB5_EZ_DATA163	0x4065068C	FULL	Memory buffer
SCB5_EZ_DATA164	0x40650690	FULL	Memory buffer
SCB5_EZ_DATA165	0x40650694	FULL	Memory buffer
SCB5_EZ_DATA166	0x40650698	FULL	Memory buffer
SCB5_EZ_DATA167	0x4065069C	FULL	Memory buffer
SCB5_EZ_DATA168	0x406506A0	FULL	Memory buffer
SCB5_EZ_DATA169	0x406506A4	FULL	Memory buffer
SCB5_EZ_DATA170	0x406506A8	FULL	Memory buffer
SCB5_EZ_DATA171	0x406506AC	FULL	Memory buffer
SCB5_EZ_DATA172	0x406506B0	FULL	Memory buffer
SCB5_EZ_DATA173	0x406506B4	FULL	Memory buffer
SCB5_EZ_DATA174	0x406506B8	FULL	Memory buffer
SCB5_EZ_DATA175	0x406506BC	FULL	Memory buffer
SCB5_EZ_DATA176	0x406506C0	FULL	Memory buffer
SCB5_EZ_DATA177	0x406506C4	FULL	Memory buffer
SCB5_EZ_DATA178	0x406506C8	FULL	Memory buffer
SCB5_EZ_DATA179	0x406506CC	FULL	Memory buffer
SCB5_EZ_DATA180	0x406506D0	FULL	Memory buffer
SCB5_EZ_DATA181	0x406506D4	FULL	Memory buffer
SCB5_EZ_DATA182	0x406506D8	FULL	Memory buffer
SCB5_EZ_DATA183	0x406506DC	FULL	Memory buffer
SCB5_EZ_DATA184	0x406506E0	FULL	Memory buffer
SCB5_EZ_DATA185	0x406506E4	FULL	Memory buffer
SCB5_EZ_DATA186	0x406506E8	FULL	Memory buffer
SCB5_EZ_DATA187	0x406506EC	FULL	Memory buffer
SCB5_EZ_DATA188	0x406506F0	FULL	Memory buffer
SCB5_EZ_DATA189	0x406506F4	FULL	Memory buffer
SCB5_EZ_DATA190	0x406506F8	FULL	Memory buffer
SCB5_EZ_DATA191	0x406506FC	FULL	Memory buffer
SCB5_EZ_DATA192	0x40650700	FULL	Memory buffer
SCB5_EZ_DATA193	0x40650704	FULL	Memory buffer
SCB5_EZ_DATA194	0x40650708	FULL	Memory buffer
SCB5_EZ_DATA195	0x4065070C	FULL	Memory buffer
SCB5_EZ_DATA196	0x40650710	FULL	Memory buffer
SCB5_EZ_DATA197	0x40650714	FULL	Memory buffer
SCB5_EZ_DATA198	0x40650718	FULL	Memory buffer
SCB5_EZ_DATA199	0x4065071C	FULL	Memory buffer
SCB5_EZ_DATA200	0x40650720	FULL	Memory buffer
SCB5_EZ_DATA201	0x40650724	FULL	Memory buffer
SCB5_EZ_DATA202	0x40650728	FULL	Memory buffer
SCB5_EZ_DATA203	0x4065072C	FULL	Memory buffer
SCB5_EZ_DATA204	0x40650730	FULL	Memory buffer
SCB5_EZ_DATA205	0x40650734	FULL	Memory buffer
SCB5_EZ_DATA206	0x40650738	FULL	Memory buffer
SCB5_EZ_DATA207	0x4065073C	FULL	Memory buffer
SCB5_EZ_DATA208	0x40650740	FULL	Memory buffer
SCB5_EZ_DATA209	0x40650744	FULL	Memory buffer
SCB5_EZ_DATA210	0x40650748	FULL	Memory buffer
SCB5_EZ_DATA211	0x4065074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB5_EZ_DATA212	0x40650750	FULL	Memory buffer
SCB5_EZ_DATA213	0x40650754	FULL	Memory buffer
SCB5_EZ_DATA214	0x40650758	FULL	Memory buffer
SCB5_EZ_DATA215	0x4065075C	FULL	Memory buffer
SCB5_EZ_DATA216	0x40650760	FULL	Memory buffer
SCB5_EZ_DATA217	0x40650764	FULL	Memory buffer
SCB5_EZ_DATA218	0x40650768	FULL	Memory buffer
SCB5_EZ_DATA219	0x4065076C	FULL	Memory buffer
SCB5_EZ_DATA220	0x40650770	FULL	Memory buffer
SCB5_EZ_DATA221	0x40650774	FULL	Memory buffer
SCB5_EZ_DATA222	0x40650778	FULL	Memory buffer
SCB5_EZ_DATA223	0x4065077C	FULL	Memory buffer
SCB5_EZ_DATA224	0x40650780	FULL	Memory buffer
SCB5_EZ_DATA225	0x40650784	FULL	Memory buffer
SCB5_EZ_DATA226	0x40650788	FULL	Memory buffer
SCB5_EZ_DATA227	0x4065078C	FULL	Memory buffer
SCB5_EZ_DATA228	0x40650790	FULL	Memory buffer
SCB5_EZ_DATA229	0x40650794	FULL	Memory buffer
SCB5_EZ_DATA230	0x40650798	FULL	Memory buffer
SCB5_EZ_DATA231	0x4065079C	FULL	Memory buffer
SCB5_EZ_DATA232	0x406507A0	FULL	Memory buffer
SCB5_EZ_DATA233	0x406507A4	FULL	Memory buffer
SCB5_EZ_DATA234	0x406507A8	FULL	Memory buffer
SCB5_EZ_DATA235	0x406507AC	FULL	Memory buffer
SCB5_EZ_DATA236	0x406507B0	FULL	Memory buffer
SCB5_EZ_DATA237	0x406507B4	FULL	Memory buffer
SCB5_EZ_DATA238	0x406507B8	FULL	Memory buffer
SCB5_EZ_DATA239	0x406507BC	FULL	Memory buffer
SCB5_EZ_DATA240	0x406507C0	FULL	Memory buffer
SCB5_EZ_DATA241	0x406507C4	FULL	Memory buffer
SCB5_EZ_DATA242	0x406507C8	FULL	Memory buffer
SCB5_EZ_DATA243	0x406507CC	FULL	Memory buffer
SCB5_EZ_DATA244	0x406507D0	FULL	Memory buffer
SCB5_EZ_DATA245	0x406507D4	FULL	Memory buffer
SCB5_EZ_DATA246	0x406507D8	FULL	Memory buffer
SCB5_EZ_DATA247	0x406507DC	FULL	Memory buffer
SCB5_EZ_DATA248	0x406507E0	FULL	Memory buffer
SCB5_EZ_DATA249	0x406507E4	FULL	Memory buffer
SCB5_EZ_DATA250	0x406507E8	FULL	Memory buffer
SCB5_EZ_DATA251	0x406507EC	FULL	Memory buffer
SCB5_EZ_DATA252	0x406507F0	FULL	Memory buffer
SCB5_EZ_DATA253	0x406507F4	FULL	Memory buffer
SCB5_EZ_DATA254	0x406507F8	FULL	Memory buffer
SCB5_EZ_DATA255	0x406507FC	FULL	Memory buffer
SCB5_INTR_CAUSE	0x40650E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB5_INTR_SPI_EC	0x40650EC0	FULL	Externally clocked SPI interrupt request
SCB5_INTR_SPI_EC_MASK	0x40650EC8	FULL	Externally clocked SPI interrupt mask
SCB5_INTR_SPI_EC_MASKED	0x40650ECC	FULL	Externally clocked SPI interrupt masked
SCB5_INTR_M	0x40650F00	FULL	Master interrupt request
SCB5_INTR_M_SET	0x40650F04	FULL	Master interrupt set request
SCB5_INTR_M_MASK	0x40650F08	FULL	Master interrupt mask
SCB5_INTR_M_MASKED	0x40650F0C	FULL	Master interrupt masked request
SCB5_INTR_S	0x40650F40	FULL	Slave interrupt request
SCB5_INTR_S_SET	0x40650F44	FULL	Slave interrupt set request
SCB5_INTR_S_MASK	0x40650F48	FULL	Slave interrupt mask
SCB5_INTR_S_MASKED	0x40650F4C	FULL	Slave interrupt masked request
SCB5_INTR_TX	0x40650F80	FULL	Transmitter interrupt request
SCB5_INTR_TX_SET	0x40650F84	FULL	Transmitter interrupt set request
SCB5_INTR_TX_MASK	0x40650F88	FULL	Transmitter interrupt mask
SCB5_INTR_TX_MASKED	0x40650F8C	FULL	Transmitter interrupt masked request
SCB5_INTR_RX	0x40650FC0	FULL	Receiver interrupt request
SCB5_INTR_RX_SET	0x40650FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB5_INTR_RX_MASK	0x40650FC8	FULL	Receiver interrupt mask
SCB5_INTR_RX_MASKED	0x40650FCC	FULL	Receiver interrupt masked request

24.7 SCB 6

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40660000

Size 0x10000

Slave Num MMIO6 - 6

Register Name	Address	Permission	Description
SCB6_CTRL	0x40660000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB6_STATUS	0x40660004	FULL	Generic status
SCB6_SPI_CTRL	0x40660020	FULL	SPI control
SCB6_SPI_STATUS	0x40660024	FULL	SPI status
SCB6_SPI_TX_CTRL	0x40660028	FULL	SPI transmitter control
SCB6_SPI_RX_CTRL	0x4066002C	FULL	SPI receiver control
SCB6_UART_CTRL	0x40660040	FULL	UART control
SCB6_UART_TX_CTRL	0x40660044	FULL	UART transmitter control
SCB6_UART_RX_CTRL	0x40660048	FULL	UART receiver control
SCB6_UART_RX_STATUS	0x4066004C	FULL	UART receiver status
SCB6_UART_FLOW_CTRL	0x40660050	FULL	UART flow control
SCB6_I2C_CTRL	0x40660060	FULL	I2C control
SCB6_I2C_STATUS	0x40660064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB6_I2C_M_CMD	0x40660068	FULL	I2C master command
SCB6_I2C_S_CMD	0x4066006C	FULL	I2C slave command
SCB6_I2C_CFG	0x40660070	FULL	I2C configuration
SCB6_TX_CTRL	0x40660200	FULL	Transmitter control
SCB6_TX_FIFO_CTRL	0x40660204	FULL	Transmitter FIFO control
SCB6_TX_FIFO_STATUS	0x40660208	FULL	Transmitter FIFO status
SCB6_TX_FIFO_WR	0x40660240	FULL	Transmitter FIFO write
SCB6_RX_CTRL	0x40660300	FULL	Receiver control
SCB6_RX_FIFO_CTRL	0x40660304	FULL	Receiver FIFO control
SCB6_RX_FIFO_STATUS	0x40660308	FULL	Receiver FIFO status
SCB6_RX_MATCH	0x40660310	FULL	Slave address and mask
SCB6_RX_FIFO_RD	0x40660340	FULL	Receiver FIFO read
SCB6_RX_FIFO_RD_SILENT	0x40660344	FULL	Receiver FIFO read silent
SCB6_EZ_DATA0	0x40660400	FULL	Memory buffer
SCB6_EZ_DATA1	0x40660404	FULL	Memory buffer
SCB6_EZ_DATA2	0x40660408	FULL	Memory buffer
SCB6_EZ_DATA3	0x4066040C	FULL	Memory buffer
SCB6_EZ_DATA4	0x40660410	FULL	Memory buffer
SCB6_EZ_DATA5	0x40660414	FULL	Memory buffer
SCB6_EZ_DATA6	0x40660418	FULL	Memory buffer
SCB6_EZ_DATA7	0x4066041C	FULL	Memory buffer
SCB6_EZ_DATA8	0x40660420	FULL	Memory buffer
SCB6_EZ_DATA9	0x40660424	FULL	Memory buffer
SCB6_EZ_DATA10	0x40660428	FULL	Memory buffer
SCB6_EZ_DATA11	0x4066042C	FULL	Memory buffer
SCB6_EZ_DATA12	0x40660430	FULL	Memory buffer
SCB6_EZ_DATA13	0x40660434	FULL	Memory buffer
SCB6_EZ_DATA14	0x40660438	FULL	Memory buffer
SCB6_EZ_DATA15	0x4066043C	FULL	Memory buffer
SCB6_EZ_DATA16	0x40660440	FULL	Memory buffer
SCB6_EZ_DATA17	0x40660444	FULL	Memory buffer
SCB6_EZ_DATA18	0x40660448	FULL	Memory buffer
SCB6_EZ_DATA19	0x4066044C	FULL	Memory buffer
SCB6_EZ_DATA20	0x40660450	FULL	Memory buffer
SCB6_EZ_DATA21	0x40660454	FULL	Memory buffer
SCB6_EZ_DATA22	0x40660458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB6_EZ_DATA23	0x4066045C	FULL	Memory buffer
SCB6_EZ_DATA24	0x40660460	FULL	Memory buffer
SCB6_EZ_DATA25	0x40660464	FULL	Memory buffer
SCB6_EZ_DATA26	0x40660468	FULL	Memory buffer
SCB6_EZ_DATA27	0x4066046C	FULL	Memory buffer
SCB6_EZ_DATA28	0x40660470	FULL	Memory buffer
SCB6_EZ_DATA29	0x40660474	FULL	Memory buffer
SCB6_EZ_DATA30	0x40660478	FULL	Memory buffer
SCB6_EZ_DATA31	0x4066047C	FULL	Memory buffer
SCB6_EZ_DATA32	0x40660480	FULL	Memory buffer
SCB6_EZ_DATA33	0x40660484	FULL	Memory buffer
SCB6_EZ_DATA34	0x40660488	FULL	Memory buffer
SCB6_EZ_DATA35	0x4066048C	FULL	Memory buffer
SCB6_EZ_DATA36	0x40660490	FULL	Memory buffer
SCB6_EZ_DATA37	0x40660494	FULL	Memory buffer
SCB6_EZ_DATA38	0x40660498	FULL	Memory buffer
SCB6_EZ_DATA39	0x4066049C	FULL	Memory buffer
SCB6_EZ_DATA40	0x406604A0	FULL	Memory buffer
SCB6_EZ_DATA41	0x406604A4	FULL	Memory buffer
SCB6_EZ_DATA42	0x406604A8	FULL	Memory buffer
SCB6_EZ_DATA43	0x406604AC	FULL	Memory buffer
SCB6_EZ_DATA44	0x406604B0	FULL	Memory buffer
SCB6_EZ_DATA45	0x406604B4	FULL	Memory buffer
SCB6_EZ_DATA46	0x406604B8	FULL	Memory buffer
SCB6_EZ_DATA47	0x406604BC	FULL	Memory buffer
SCB6_EZ_DATA48	0x406604C0	FULL	Memory buffer
SCB6_EZ_DATA49	0x406604C4	FULL	Memory buffer
SCB6_EZ_DATA50	0x406604C8	FULL	Memory buffer
SCB6_EZ_DATA51	0x406604CC	FULL	Memory buffer
SCB6_EZ_DATA52	0x406604D0	FULL	Memory buffer
SCB6_EZ_DATA53	0x406604D4	FULL	Memory buffer
SCB6_EZ_DATA54	0x406604D8	FULL	Memory buffer
SCB6_EZ_DATA55	0x406604DC	FULL	Memory buffer
SCB6_EZ_DATA56	0x406604E0	FULL	Memory buffer
SCB6_EZ_DATA57	0x406604E4	FULL	Memory buffer
SCB6_EZ_DATA58	0x406604E8	FULL	Memory buffer
SCB6_EZ_DATA59	0x406604EC	FULL	Memory buffer
SCB6_EZ_DATA60	0x406604F0	FULL	Memory buffer
SCB6_EZ_DATA61	0x406604F4	FULL	Memory buffer
SCB6_EZ_DATA62	0x406604F8	FULL	Memory buffer
SCB6_EZ_DATA63	0x406604FC	FULL	Memory buffer
SCB6_EZ_DATA64	0x40660500	FULL	Memory buffer
SCB6_EZ_DATA65	0x40660504	FULL	Memory buffer
SCB6_EZ_DATA66	0x40660508	FULL	Memory buffer
SCB6_EZ_DATA67	0x4066050C	FULL	Memory buffer
SCB6_EZ_DATA68	0x40660510	FULL	Memory buffer
SCB6_EZ_DATA69	0x40660514	FULL	Memory buffer
SCB6_EZ_DATA70	0x40660518	FULL	Memory buffer
SCB6_EZ_DATA71	0x4066051C	FULL	Memory buffer
SCB6_EZ_DATA72	0x40660520	FULL	Memory buffer
SCB6_EZ_DATA73	0x40660524	FULL	Memory buffer
SCB6_EZ_DATA74	0x40660528	FULL	Memory buffer
SCB6_EZ_DATA75	0x4066052C	FULL	Memory buffer
SCB6_EZ_DATA76	0x40660530	FULL	Memory buffer
SCB6_EZ_DATA77	0x40660534	FULL	Memory buffer
SCB6_EZ_DATA78	0x40660538	FULL	Memory buffer
SCB6_EZ_DATA79	0x4066053C	FULL	Memory buffer
SCB6_EZ_DATA80	0x40660540	FULL	Memory buffer
SCB6_EZ_DATA81	0x40660544	FULL	Memory buffer
SCB6_EZ_DATA82	0x40660548	FULL	Memory buffer
SCB6_EZ_DATA83	0x4066054C	FULL	Memory buffer
SCB6_EZ_DATA84	0x40660550	FULL	Memory buffer
SCB6_EZ_DATA85	0x40660554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB6_EZ_DATA86	0x40660558	FULL	Memory buffer
SCB6_EZ_DATA87	0x4066055C	FULL	Memory buffer
SCB6_EZ_DATA88	0x40660560	FULL	Memory buffer
SCB6_EZ_DATA89	0x40660564	FULL	Memory buffer
SCB6_EZ_DATA90	0x40660568	FULL	Memory buffer
SCB6_EZ_DATA91	0x4066056C	FULL	Memory buffer
SCB6_EZ_DATA92	0x40660570	FULL	Memory buffer
SCB6_EZ_DATA93	0x40660574	FULL	Memory buffer
SCB6_EZ_DATA94	0x40660578	FULL	Memory buffer
SCB6_EZ_DATA95	0x4066057C	FULL	Memory buffer
SCB6_EZ_DATA96	0x40660580	FULL	Memory buffer
SCB6_EZ_DATA97	0x40660584	FULL	Memory buffer
SCB6_EZ_DATA98	0x40660588	FULL	Memory buffer
SCB6_EZ_DATA99	0x4066058C	FULL	Memory buffer
SCB6_EZ_DATA100	0x40660590	FULL	Memory buffer
SCB6_EZ_DATA101	0x40660594	FULL	Memory buffer
SCB6_EZ_DATA102	0x40660598	FULL	Memory buffer
SCB6_EZ_DATA103	0x4066059C	FULL	Memory buffer
SCB6_EZ_DATA104	0x406605A0	FULL	Memory buffer
SCB6_EZ_DATA105	0x406605A4	FULL	Memory buffer
SCB6_EZ_DATA106	0x406605A8	FULL	Memory buffer
SCB6_EZ_DATA107	0x406605AC	FULL	Memory buffer
SCB6_EZ_DATA108	0x406605B0	FULL	Memory buffer
SCB6_EZ_DATA109	0x406605B4	FULL	Memory buffer
SCB6_EZ_DATA110	0x406605B8	FULL	Memory buffer
SCB6_EZ_DATA111	0x406605BC	FULL	Memory buffer
SCB6_EZ_DATA112	0x406605C0	FULL	Memory buffer
SCB6_EZ_DATA113	0x406605C4	FULL	Memory buffer
SCB6_EZ_DATA114	0x406605C8	FULL	Memory buffer
SCB6_EZ_DATA115	0x406605CC	FULL	Memory buffer
SCB6_EZ_DATA116	0x406605D0	FULL	Memory buffer
SCB6_EZ_DATA117	0x406605D4	FULL	Memory buffer
SCB6_EZ_DATA118	0x406605D8	FULL	Memory buffer
SCB6_EZ_DATA119	0x406605DC	FULL	Memory buffer
SCB6_EZ_DATA120	0x406605E0	FULL	Memory buffer
SCB6_EZ_DATA121	0x406605E4	FULL	Memory buffer
SCB6_EZ_DATA122	0x406605E8	FULL	Memory buffer
SCB6_EZ_DATA123	0x406605EC	FULL	Memory buffer
SCB6_EZ_DATA124	0x406605F0	FULL	Memory buffer
SCB6_EZ_DATA125	0x406605F4	FULL	Memory buffer
SCB6_EZ_DATA126	0x406605F8	FULL	Memory buffer
SCB6_EZ_DATA127	0x406605FC	FULL	Memory buffer
SCB6_EZ_DATA128	0x40660600	FULL	Memory buffer
SCB6_EZ_DATA129	0x40660604	FULL	Memory buffer
SCB6_EZ_DATA130	0x40660608	FULL	Memory buffer
SCB6_EZ_DATA131	0x4066060C	FULL	Memory buffer
SCB6_EZ_DATA132	0x40660610	FULL	Memory buffer
SCB6_EZ_DATA133	0x40660614	FULL	Memory buffer
SCB6_EZ_DATA134	0x40660618	FULL	Memory buffer
SCB6_EZ_DATA135	0x4066061C	FULL	Memory buffer
SCB6_EZ_DATA136	0x40660620	FULL	Memory buffer
SCB6_EZ_DATA137	0x40660624	FULL	Memory buffer
SCB6_EZ_DATA138	0x40660628	FULL	Memory buffer
SCB6_EZ_DATA139	0x4066062C	FULL	Memory buffer
SCB6_EZ_DATA140	0x40660630	FULL	Memory buffer
SCB6_EZ_DATA141	0x40660634	FULL	Memory buffer
SCB6_EZ_DATA142	0x40660638	FULL	Memory buffer
SCB6_EZ_DATA143	0x4066063C	FULL	Memory buffer
SCB6_EZ_DATA144	0x40660640	FULL	Memory buffer
SCB6_EZ_DATA145	0x40660644	FULL	Memory buffer
SCB6_EZ_DATA146	0x40660648	FULL	Memory buffer
SCB6_EZ_DATA147	0x4066064C	FULL	Memory buffer
SCB6_EZ_DATA148	0x40660650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB6_EZ_DATA149	0x40660654	FULL	Memory buffer
SCB6_EZ_DATA150	0x40660658	FULL	Memory buffer
SCB6_EZ_DATA151	0x4066065C	FULL	Memory buffer
SCB6_EZ_DATA152	0x40660660	FULL	Memory buffer
SCB6_EZ_DATA153	0x40660664	FULL	Memory buffer
SCB6_EZ_DATA154	0x40660668	FULL	Memory buffer
SCB6_EZ_DATA155	0x4066066C	FULL	Memory buffer
SCB6_EZ_DATA156	0x40660670	FULL	Memory buffer
SCB6_EZ_DATA157	0x40660674	FULL	Memory buffer
SCB6_EZ_DATA158	0x40660678	FULL	Memory buffer
SCB6_EZ_DATA159	0x4066067C	FULL	Memory buffer
SCB6_EZ_DATA160	0x40660680	FULL	Memory buffer
SCB6_EZ_DATA161	0x40660684	FULL	Memory buffer
SCB6_EZ_DATA162	0x40660688	FULL	Memory buffer
SCB6_EZ_DATA163	0x4066068C	FULL	Memory buffer
SCB6_EZ_DATA164	0x40660690	FULL	Memory buffer
SCB6_EZ_DATA165	0x40660694	FULL	Memory buffer
SCB6_EZ_DATA166	0x40660698	FULL	Memory buffer
SCB6_EZ_DATA167	0x4066069C	FULL	Memory buffer
SCB6_EZ_DATA168	0x406606A0	FULL	Memory buffer
SCB6_EZ_DATA169	0x406606A4	FULL	Memory buffer
SCB6_EZ_DATA170	0x406606A8	FULL	Memory buffer
SCB6_EZ_DATA171	0x406606AC	FULL	Memory buffer
SCB6_EZ_DATA172	0x406606B0	FULL	Memory buffer
SCB6_EZ_DATA173	0x406606B4	FULL	Memory buffer
SCB6_EZ_DATA174	0x406606B8	FULL	Memory buffer
SCB6_EZ_DATA175	0x406606BC	FULL	Memory buffer
SCB6_EZ_DATA176	0x406606C0	FULL	Memory buffer
SCB6_EZ_DATA177	0x406606C4	FULL	Memory buffer
SCB6_EZ_DATA178	0x406606C8	FULL	Memory buffer
SCB6_EZ_DATA179	0x406606CC	FULL	Memory buffer
SCB6_EZ_DATA180	0x406606D0	FULL	Memory buffer
SCB6_EZ_DATA181	0x406606D4	FULL	Memory buffer
SCB6_EZ_DATA182	0x406606D8	FULL	Memory buffer
SCB6_EZ_DATA183	0x406606DC	FULL	Memory buffer
SCB6_EZ_DATA184	0x406606E0	FULL	Memory buffer
SCB6_EZ_DATA185	0x406606E4	FULL	Memory buffer
SCB6_EZ_DATA186	0x406606E8	FULL	Memory buffer
SCB6_EZ_DATA187	0x406606EC	FULL	Memory buffer
SCB6_EZ_DATA188	0x406606F0	FULL	Memory buffer
SCB6_EZ_DATA189	0x406606F4	FULL	Memory buffer
SCB6_EZ_DATA190	0x406606F8	FULL	Memory buffer
SCB6_EZ_DATA191	0x406606FC	FULL	Memory buffer
SCB6_EZ_DATA192	0x40660700	FULL	Memory buffer
SCB6_EZ_DATA193	0x40660704	FULL	Memory buffer
SCB6_EZ_DATA194	0x40660708	FULL	Memory buffer
SCB6_EZ_DATA195	0x4066070C	FULL	Memory buffer
SCB6_EZ_DATA196	0x40660710	FULL	Memory buffer
SCB6_EZ_DATA197	0x40660714	FULL	Memory buffer
SCB6_EZ_DATA198	0x40660718	FULL	Memory buffer
SCB6_EZ_DATA199	0x4066071C	FULL	Memory buffer
SCB6_EZ_DATA200	0x40660720	FULL	Memory buffer
SCB6_EZ_DATA201	0x40660724	FULL	Memory buffer
SCB6_EZ_DATA202	0x40660728	FULL	Memory buffer
SCB6_EZ_DATA203	0x4066072C	FULL	Memory buffer
SCB6_EZ_DATA204	0x40660730	FULL	Memory buffer
SCB6_EZ_DATA205	0x40660734	FULL	Memory buffer
SCB6_EZ_DATA206	0x40660738	FULL	Memory buffer
SCB6_EZ_DATA207	0x4066073C	FULL	Memory buffer
SCB6_EZ_DATA208	0x40660740	FULL	Memory buffer
SCB6_EZ_DATA209	0x40660744	FULL	Memory buffer
SCB6_EZ_DATA210	0x40660748	FULL	Memory buffer
SCB6_EZ_DATA211	0x4066074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB6_EZ_DATA212	0x40660750	FULL	Memory buffer
SCB6_EZ_DATA213	0x40660754	FULL	Memory buffer
SCB6_EZ_DATA214	0x40660758	FULL	Memory buffer
SCB6_EZ_DATA215	0x4066075C	FULL	Memory buffer
SCB6_EZ_DATA216	0x40660760	FULL	Memory buffer
SCB6_EZ_DATA217	0x40660764	FULL	Memory buffer
SCB6_EZ_DATA218	0x40660768	FULL	Memory buffer
SCB6_EZ_DATA219	0x4066076C	FULL	Memory buffer
SCB6_EZ_DATA220	0x40660770	FULL	Memory buffer
SCB6_EZ_DATA221	0x40660774	FULL	Memory buffer
SCB6_EZ_DATA222	0x40660778	FULL	Memory buffer
SCB6_EZ_DATA223	0x4066077C	FULL	Memory buffer
SCB6_EZ_DATA224	0x40660780	FULL	Memory buffer
SCB6_EZ_DATA225	0x40660784	FULL	Memory buffer
SCB6_EZ_DATA226	0x40660788	FULL	Memory buffer
SCB6_EZ_DATA227	0x4066078C	FULL	Memory buffer
SCB6_EZ_DATA228	0x40660790	FULL	Memory buffer
SCB6_EZ_DATA229	0x40660794	FULL	Memory buffer
SCB6_EZ_DATA230	0x40660798	FULL	Memory buffer
SCB6_EZ_DATA231	0x4066079C	FULL	Memory buffer
SCB6_EZ_DATA232	0x406607A0	FULL	Memory buffer
SCB6_EZ_DATA233	0x406607A4	FULL	Memory buffer
SCB6_EZ_DATA234	0x406607A8	FULL	Memory buffer
SCB6_EZ_DATA235	0x406607AC	FULL	Memory buffer
SCB6_EZ_DATA236	0x406607B0	FULL	Memory buffer
SCB6_EZ_DATA237	0x406607B4	FULL	Memory buffer
SCB6_EZ_DATA238	0x406607B8	FULL	Memory buffer
SCB6_EZ_DATA239	0x406607BC	FULL	Memory buffer
SCB6_EZ_DATA240	0x406607C0	FULL	Memory buffer
SCB6_EZ_DATA241	0x406607C4	FULL	Memory buffer
SCB6_EZ_DATA242	0x406607C8	FULL	Memory buffer
SCB6_EZ_DATA243	0x406607CC	FULL	Memory buffer
SCB6_EZ_DATA244	0x406607D0	FULL	Memory buffer
SCB6_EZ_DATA245	0x406607D4	FULL	Memory buffer
SCB6_EZ_DATA246	0x406607D8	FULL	Memory buffer
SCB6_EZ_DATA247	0x406607DC	FULL	Memory buffer
SCB6_EZ_DATA248	0x406607E0	FULL	Memory buffer
SCB6_EZ_DATA249	0x406607E4	FULL	Memory buffer
SCB6_EZ_DATA250	0x406607E8	FULL	Memory buffer
SCB6_EZ_DATA251	0x406607EC	FULL	Memory buffer
SCB6_EZ_DATA252	0x406607F0	FULL	Memory buffer
SCB6_EZ_DATA253	0x406607F4	FULL	Memory buffer
SCB6_EZ_DATA254	0x406607F8	FULL	Memory buffer
SCB6_EZ_DATA255	0x406607FC	FULL	Memory buffer
SCB6_INTR_CAUSE	0x40660E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB6_INTR_SPI_EC	0x40660EC0	FULL	Externally clocked SPI interrupt request
SCB6_INTR_SPI_EC_MASK	0x40660EC8	FULL	Externally clocked SPI interrupt mask
SCB6_INTR_SPI_EC_MASKED	0x40660ECC	FULL	Externally clocked SPI interrupt masked
SCB6_INTR_M	0x40660F00	FULL	Master interrupt request
SCB6_INTR_M_SET	0x40660F04	FULL	Master interrupt set request
SCB6_INTR_M_MASK	0x40660F08	FULL	Master interrupt mask
SCB6_INTR_M_MASKED	0x40660F0C	FULL	Master interrupt masked request
SCB6_INTR_S	0x40660F40	FULL	Slave interrupt request
SCB6_INTR_S_SET	0x40660F44	FULL	Slave interrupt set request
SCB6_INTR_S_MASK	0x40660F48	FULL	Slave interrupt mask
SCB6_INTR_S_MASKED	0x40660F4C	FULL	Slave interrupt masked request
SCB6_INTR_TX	0x40660F80	FULL	Transmitter interrupt request
SCB6_INTR_TX_SET	0x40660F84	FULL	Transmitter interrupt set request
SCB6_INTR_TX_MASK	0x40660F88	FULL	Transmitter interrupt mask
SCB6_INTR_TX_MASKED	0x40660F8C	FULL	Transmitter interrupt masked request
SCB6_INTR_RX	0x40660FC0	FULL	Receiver interrupt request
SCB6_INTR_RX_SET	0x40660FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB6_INTR_RX_MASK	0x40660FC8	FULL	Receiver interrupt mask
SCB6_INTR_RX_MASKED	0x40660FCC	FULL	Receiver interrupt masked request

24.8 SCB 7

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40670000

Size 0x10000

Slave Num MMIO6 - 7

Register Name	Address	Permission	Description
SCB7_CTRL	0x40670000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB7_STATUS	0x40670004	FULL	Generic status
SCB7_SPI_CTRL	0x40670020	FULL	SPI control
SCB7_SPI_STATUS	0x40670024	FULL	SPI status
SCB7_SPI_TX_CTRL	0x40670028	FULL	SPI transmitter control
SCB7_SPI_RX_CTRL	0x4067002C	FULL	SPI receiver control
SCB7_UART_CTRL	0x40670040	FULL	UART control
SCB7_UART_TX_CTRL	0x40670044	FULL	UART transmitter control
SCB7_UART_RX_CTRL	0x40670048	FULL	UART receiver control
SCB7_UART_RX_STATUS	0x4067004C	FULL	UART receiver status
SCB7_UART_FLOW_CTRL	0x40670050	FULL	UART flow control
SCB7_I2C_CTRL	0x40670060	FULL	I2C control
SCB7_I2C_STATUS	0x40670064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB7_I2C_M_CMD	0x40670068	FULL	I2C master command
SCB7_I2C_S_CMD	0x4067006C	FULL	I2C slave command
SCB7_I2C_CFG	0x40670070	FULL	I2C configuration
SCB7_TX_CTRL	0x40670200	FULL	Transmitter control
SCB7_TX_FIFO_CTRL	0x40670204	FULL	Transmitter FIFO control
SCB7_TX_FIFO_STATUS	0x40670208	FULL	Transmitter FIFO status
SCB7_TX_FIFO_WR	0x40670240	FULL	Transmitter FIFO write
SCB7_RX_CTRL	0x40670300	FULL	Receiver control
SCB7_RX_FIFO_CTRL	0x40670304	FULL	Receiver FIFO control
SCB7_RX_FIFO_STATUS	0x40670308	FULL	Receiver FIFO status
SCB7_RX_MATCH	0x40670310	FULL	Slave address and mask
SCB7_RX_FIFO_RD	0x40670340	FULL	Receiver FIFO read
SCB7_RX_FIFO_RD_SILENT	0x40670344	FULL	Receiver FIFO read silent
SCB7_EZ_DATA0	0x40670400	FULL	Memory buffer
SCB7_EZ_DATA1	0x40670404	FULL	Memory buffer
SCB7_EZ_DATA2	0x40670408	FULL	Memory buffer
SCB7_EZ_DATA3	0x4067040C	FULL	Memory buffer
SCB7_EZ_DATA4	0x40670410	FULL	Memory buffer
SCB7_EZ_DATA5	0x40670414	FULL	Memory buffer
SCB7_EZ_DATA6	0x40670418	FULL	Memory buffer
SCB7_EZ_DATA7	0x4067041C	FULL	Memory buffer
SCB7_EZ_DATA8	0x40670420	FULL	Memory buffer
SCB7_EZ_DATA9	0x40670424	FULL	Memory buffer
SCB7_EZ_DATA10	0x40670428	FULL	Memory buffer
SCB7_EZ_DATA11	0x4067042C	FULL	Memory buffer
SCB7_EZ_DATA12	0x40670430	FULL	Memory buffer
SCB7_EZ_DATA13	0x40670434	FULL	Memory buffer
SCB7_EZ_DATA14	0x40670438	FULL	Memory buffer
SCB7_EZ_DATA15	0x4067043C	FULL	Memory buffer
SCB7_EZ_DATA16	0x40670440	FULL	Memory buffer
SCB7_EZ_DATA17	0x40670444	FULL	Memory buffer
SCB7_EZ_DATA18	0x40670448	FULL	Memory buffer
SCB7_EZ_DATA19	0x4067044C	FULL	Memory buffer
SCB7_EZ_DATA20	0x40670450	FULL	Memory buffer
SCB7_EZ_DATA21	0x40670454	FULL	Memory buffer
SCB7_EZ_DATA22	0x40670458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB7_EZ_DATA23	0x4067045C	FULL	Memory buffer
SCB7_EZ_DATA24	0x40670460	FULL	Memory buffer
SCB7_EZ_DATA25	0x40670464	FULL	Memory buffer
SCB7_EZ_DATA26	0x40670468	FULL	Memory buffer
SCB7_EZ_DATA27	0x4067046C	FULL	Memory buffer
SCB7_EZ_DATA28	0x40670470	FULL	Memory buffer
SCB7_EZ_DATA29	0x40670474	FULL	Memory buffer
SCB7_EZ_DATA30	0x40670478	FULL	Memory buffer
SCB7_EZ_DATA31	0x4067047C	FULL	Memory buffer
SCB7_EZ_DATA32	0x40670480	FULL	Memory buffer
SCB7_EZ_DATA33	0x40670484	FULL	Memory buffer
SCB7_EZ_DATA34	0x40670488	FULL	Memory buffer
SCB7_EZ_DATA35	0x4067048C	FULL	Memory buffer
SCB7_EZ_DATA36	0x40670490	FULL	Memory buffer
SCB7_EZ_DATA37	0x40670494	FULL	Memory buffer
SCB7_EZ_DATA38	0x40670498	FULL	Memory buffer
SCB7_EZ_DATA39	0x4067049C	FULL	Memory buffer
SCB7_EZ_DATA40	0x406704A0	FULL	Memory buffer
SCB7_EZ_DATA41	0x406704A4	FULL	Memory buffer
SCB7_EZ_DATA42	0x406704A8	FULL	Memory buffer
SCB7_EZ_DATA43	0x406704AC	FULL	Memory buffer
SCB7_EZ_DATA44	0x406704B0	FULL	Memory buffer
SCB7_EZ_DATA45	0x406704B4	FULL	Memory buffer
SCB7_EZ_DATA46	0x406704B8	FULL	Memory buffer
SCB7_EZ_DATA47	0x406704BC	FULL	Memory buffer
SCB7_EZ_DATA48	0x406704C0	FULL	Memory buffer
SCB7_EZ_DATA49	0x406704C4	FULL	Memory buffer
SCB7_EZ_DATA50	0x406704C8	FULL	Memory buffer
SCB7_EZ_DATA51	0x406704CC	FULL	Memory buffer
SCB7_EZ_DATA52	0x406704D0	FULL	Memory buffer
SCB7_EZ_DATA53	0x406704D4	FULL	Memory buffer
SCB7_EZ_DATA54	0x406704D8	FULL	Memory buffer
SCB7_EZ_DATA55	0x406704DC	FULL	Memory buffer
SCB7_EZ_DATA56	0x406704E0	FULL	Memory buffer
SCB7_EZ_DATA57	0x406704E4	FULL	Memory buffer
SCB7_EZ_DATA58	0x406704E8	FULL	Memory buffer
SCB7_EZ_DATA59	0x406704EC	FULL	Memory buffer
SCB7_EZ_DATA60	0x406704F0	FULL	Memory buffer
SCB7_EZ_DATA61	0x406704F4	FULL	Memory buffer
SCB7_EZ_DATA62	0x406704F8	FULL	Memory buffer
SCB7_EZ_DATA63	0x406704FC	FULL	Memory buffer
SCB7_EZ_DATA64	0x40670500	FULL	Memory buffer
SCB7_EZ_DATA65	0x40670504	FULL	Memory buffer
SCB7_EZ_DATA66	0x40670508	FULL	Memory buffer
SCB7_EZ_DATA67	0x4067050C	FULL	Memory buffer
SCB7_EZ_DATA68	0x40670510	FULL	Memory buffer
SCB7_EZ_DATA69	0x40670514	FULL	Memory buffer
SCB7_EZ_DATA70	0x40670518	FULL	Memory buffer
SCB7_EZ_DATA71	0x4067051C	FULL	Memory buffer
SCB7_EZ_DATA72	0x40670520	FULL	Memory buffer
SCB7_EZ_DATA73	0x40670524	FULL	Memory buffer
SCB7_EZ_DATA74	0x40670528	FULL	Memory buffer
SCB7_EZ_DATA75	0x4067052C	FULL	Memory buffer
SCB7_EZ_DATA76	0x40670530	FULL	Memory buffer
SCB7_EZ_DATA77	0x40670534	FULL	Memory buffer
SCB7_EZ_DATA78	0x40670538	FULL	Memory buffer
SCB7_EZ_DATA79	0x4067053C	FULL	Memory buffer
SCB7_EZ_DATA80	0x40670540	FULL	Memory buffer
SCB7_EZ_DATA81	0x40670544	FULL	Memory buffer
SCB7_EZ_DATA82	0x40670548	FULL	Memory buffer
SCB7_EZ_DATA83	0x4067054C	FULL	Memory buffer
SCB7_EZ_DATA84	0x40670550	FULL	Memory buffer
SCB7_EZ_DATA85	0x40670554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB7_EZ_DATA86	0x40670558	FULL	Memory buffer
SCB7_EZ_DATA87	0x4067055C	FULL	Memory buffer
SCB7_EZ_DATA88	0x40670560	FULL	Memory buffer
SCB7_EZ_DATA89	0x40670564	FULL	Memory buffer
SCB7_EZ_DATA90	0x40670568	FULL	Memory buffer
SCB7_EZ_DATA91	0x4067056C	FULL	Memory buffer
SCB7_EZ_DATA92	0x40670570	FULL	Memory buffer
SCB7_EZ_DATA93	0x40670574	FULL	Memory buffer
SCB7_EZ_DATA94	0x40670578	FULL	Memory buffer
SCB7_EZ_DATA95	0x4067057C	FULL	Memory buffer
SCB7_EZ_DATA96	0x40670580	FULL	Memory buffer
SCB7_EZ_DATA97	0x40670584	FULL	Memory buffer
SCB7_EZ_DATA98	0x40670588	FULL	Memory buffer
SCB7_EZ_DATA99	0x4067058C	FULL	Memory buffer
SCB7_EZ_DATA100	0x40670590	FULL	Memory buffer
SCB7_EZ_DATA101	0x40670594	FULL	Memory buffer
SCB7_EZ_DATA102	0x40670598	FULL	Memory buffer
SCB7_EZ_DATA103	0x4067059C	FULL	Memory buffer
SCB7_EZ_DATA104	0x406705A0	FULL	Memory buffer
SCB7_EZ_DATA105	0x406705A4	FULL	Memory buffer
SCB7_EZ_DATA106	0x406705A8	FULL	Memory buffer
SCB7_EZ_DATA107	0x406705AC	FULL	Memory buffer
SCB7_EZ_DATA108	0x406705B0	FULL	Memory buffer
SCB7_EZ_DATA109	0x406705B4	FULL	Memory buffer
SCB7_EZ_DATA110	0x406705B8	FULL	Memory buffer
SCB7_EZ_DATA111	0x406705BC	FULL	Memory buffer
SCB7_EZ_DATA112	0x406705C0	FULL	Memory buffer
SCB7_EZ_DATA113	0x406705C4	FULL	Memory buffer
SCB7_EZ_DATA114	0x406705C8	FULL	Memory buffer
SCB7_EZ_DATA115	0x406705CC	FULL	Memory buffer
SCB7_EZ_DATA116	0x406705D0	FULL	Memory buffer
SCB7_EZ_DATA117	0x406705D4	FULL	Memory buffer
SCB7_EZ_DATA118	0x406705D8	FULL	Memory buffer
SCB7_EZ_DATA119	0x406705DC	FULL	Memory buffer
SCB7_EZ_DATA120	0x406705E0	FULL	Memory buffer
SCB7_EZ_DATA121	0x406705E4	FULL	Memory buffer
SCB7_EZ_DATA122	0x406705E8	FULL	Memory buffer
SCB7_EZ_DATA123	0x406705EC	FULL	Memory buffer
SCB7_EZ_DATA124	0x406705F0	FULL	Memory buffer
SCB7_EZ_DATA125	0x406705F4	FULL	Memory buffer
SCB7_EZ_DATA126	0x406705F8	FULL	Memory buffer
SCB7_EZ_DATA127	0x406705FC	FULL	Memory buffer
SCB7_EZ_DATA128	0x40670600	FULL	Memory buffer
SCB7_EZ_DATA129	0x40670604	FULL	Memory buffer
SCB7_EZ_DATA130	0x40670608	FULL	Memory buffer
SCB7_EZ_DATA131	0x4067060C	FULL	Memory buffer
SCB7_EZ_DATA132	0x40670610	FULL	Memory buffer
SCB7_EZ_DATA133	0x40670614	FULL	Memory buffer
SCB7_EZ_DATA134	0x40670618	FULL	Memory buffer
SCB7_EZ_DATA135	0x4067061C	FULL	Memory buffer
SCB7_EZ_DATA136	0x40670620	FULL	Memory buffer
SCB7_EZ_DATA137	0x40670624	FULL	Memory buffer
SCB7_EZ_DATA138	0x40670628	FULL	Memory buffer
SCB7_EZ_DATA139	0x4067062C	FULL	Memory buffer
SCB7_EZ_DATA140	0x40670630	FULL	Memory buffer
SCB7_EZ_DATA141	0x40670634	FULL	Memory buffer
SCB7_EZ_DATA142	0x40670638	FULL	Memory buffer
SCB7_EZ_DATA143	0x4067063C	FULL	Memory buffer
SCB7_EZ_DATA144	0x40670640	FULL	Memory buffer
SCB7_EZ_DATA145	0x40670644	FULL	Memory buffer
SCB7_EZ_DATA146	0x40670648	FULL	Memory buffer
SCB7_EZ_DATA147	0x4067064C	FULL	Memory buffer
SCB7_EZ_DATA148	0x40670650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB7_EZ_DATA149	0x40670654	FULL	Memory buffer
SCB7_EZ_DATA150	0x40670658	FULL	Memory buffer
SCB7_EZ_DATA151	0x4067065C	FULL	Memory buffer
SCB7_EZ_DATA152	0x40670660	FULL	Memory buffer
SCB7_EZ_DATA153	0x40670664	FULL	Memory buffer
SCB7_EZ_DATA154	0x40670668	FULL	Memory buffer
SCB7_EZ_DATA155	0x4067066C	FULL	Memory buffer
SCB7_EZ_DATA156	0x40670670	FULL	Memory buffer
SCB7_EZ_DATA157	0x40670674	FULL	Memory buffer
SCB7_EZ_DATA158	0x40670678	FULL	Memory buffer
SCB7_EZ_DATA159	0x4067067C	FULL	Memory buffer
SCB7_EZ_DATA160	0x40670680	FULL	Memory buffer
SCB7_EZ_DATA161	0x40670684	FULL	Memory buffer
SCB7_EZ_DATA162	0x40670688	FULL	Memory buffer
SCB7_EZ_DATA163	0x4067068C	FULL	Memory buffer
SCB7_EZ_DATA164	0x40670690	FULL	Memory buffer
SCB7_EZ_DATA165	0x40670694	FULL	Memory buffer
SCB7_EZ_DATA166	0x40670698	FULL	Memory buffer
SCB7_EZ_DATA167	0x4067069C	FULL	Memory buffer
SCB7_EZ_DATA168	0x406706A0	FULL	Memory buffer
SCB7_EZ_DATA169	0x406706A4	FULL	Memory buffer
SCB7_EZ_DATA170	0x406706A8	FULL	Memory buffer
SCB7_EZ_DATA171	0x406706AC	FULL	Memory buffer
SCB7_EZ_DATA172	0x406706B0	FULL	Memory buffer
SCB7_EZ_DATA173	0x406706B4	FULL	Memory buffer
SCB7_EZ_DATA174	0x406706B8	FULL	Memory buffer
SCB7_EZ_DATA175	0x406706BC	FULL	Memory buffer
SCB7_EZ_DATA176	0x406706C0	FULL	Memory buffer
SCB7_EZ_DATA177	0x406706C4	FULL	Memory buffer
SCB7_EZ_DATA178	0x406706C8	FULL	Memory buffer
SCB7_EZ_DATA179	0x406706CC	FULL	Memory buffer
SCB7_EZ_DATA180	0x406706D0	FULL	Memory buffer
SCB7_EZ_DATA181	0x406706D4	FULL	Memory buffer
SCB7_EZ_DATA182	0x406706D8	FULL	Memory buffer
SCB7_EZ_DATA183	0x406706DC	FULL	Memory buffer
SCB7_EZ_DATA184	0x406706E0	FULL	Memory buffer
SCB7_EZ_DATA185	0x406706E4	FULL	Memory buffer
SCB7_EZ_DATA186	0x406706E8	FULL	Memory buffer
SCB7_EZ_DATA187	0x406706EC	FULL	Memory buffer
SCB7_EZ_DATA188	0x406706F0	FULL	Memory buffer
SCB7_EZ_DATA189	0x406706F4	FULL	Memory buffer
SCB7_EZ_DATA190	0x406706F8	FULL	Memory buffer
SCB7_EZ_DATA191	0x406706FC	FULL	Memory buffer
SCB7_EZ_DATA192	0x40670700	FULL	Memory buffer
SCB7_EZ_DATA193	0x40670704	FULL	Memory buffer
SCB7_EZ_DATA194	0x40670708	FULL	Memory buffer
SCB7_EZ_DATA195	0x4067070C	FULL	Memory buffer
SCB7_EZ_DATA196	0x40670710	FULL	Memory buffer
SCB7_EZ_DATA197	0x40670714	FULL	Memory buffer
SCB7_EZ_DATA198	0x40670718	FULL	Memory buffer
SCB7_EZ_DATA199	0x4067071C	FULL	Memory buffer
SCB7_EZ_DATA200	0x40670720	FULL	Memory buffer
SCB7_EZ_DATA201	0x40670724	FULL	Memory buffer
SCB7_EZ_DATA202	0x40670728	FULL	Memory buffer
SCB7_EZ_DATA203	0x4067072C	FULL	Memory buffer
SCB7_EZ_DATA204	0x40670730	FULL	Memory buffer
SCB7_EZ_DATA205	0x40670734	FULL	Memory buffer
SCB7_EZ_DATA206	0x40670738	FULL	Memory buffer
SCB7_EZ_DATA207	0x4067073C	FULL	Memory buffer
SCB7_EZ_DATA208	0x40670740	FULL	Memory buffer
SCB7_EZ_DATA209	0x40670744	FULL	Memory buffer
SCB7_EZ_DATA210	0x40670748	FULL	Memory buffer
SCB7_EZ_DATA211	0x4067074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB7_EZ_DATA212	0x40670750	FULL	Memory buffer
SCB7_EZ_DATA213	0x40670754	FULL	Memory buffer
SCB7_EZ_DATA214	0x40670758	FULL	Memory buffer
SCB7_EZ_DATA215	0x4067075C	FULL	Memory buffer
SCB7_EZ_DATA216	0x40670760	FULL	Memory buffer
SCB7_EZ_DATA217	0x40670764	FULL	Memory buffer
SCB7_EZ_DATA218	0x40670768	FULL	Memory buffer
SCB7_EZ_DATA219	0x4067076C	FULL	Memory buffer
SCB7_EZ_DATA220	0x40670770	FULL	Memory buffer
SCB7_EZ_DATA221	0x40670774	FULL	Memory buffer
SCB7_EZ_DATA222	0x40670778	FULL	Memory buffer
SCB7_EZ_DATA223	0x4067077C	FULL	Memory buffer
SCB7_EZ_DATA224	0x40670780	FULL	Memory buffer
SCB7_EZ_DATA225	0x40670784	FULL	Memory buffer
SCB7_EZ_DATA226	0x40670788	FULL	Memory buffer
SCB7_EZ_DATA227	0x4067078C	FULL	Memory buffer
SCB7_EZ_DATA228	0x40670790	FULL	Memory buffer
SCB7_EZ_DATA229	0x40670794	FULL	Memory buffer
SCB7_EZ_DATA230	0x40670798	FULL	Memory buffer
SCB7_EZ_DATA231	0x4067079C	FULL	Memory buffer
SCB7_EZ_DATA232	0x406707A0	FULL	Memory buffer
SCB7_EZ_DATA233	0x406707A4	FULL	Memory buffer
SCB7_EZ_DATA234	0x406707A8	FULL	Memory buffer
SCB7_EZ_DATA235	0x406707AC	FULL	Memory buffer
SCB7_EZ_DATA236	0x406707B0	FULL	Memory buffer
SCB7_EZ_DATA237	0x406707B4	FULL	Memory buffer
SCB7_EZ_DATA238	0x406707B8	FULL	Memory buffer
SCB7_EZ_DATA239	0x406707BC	FULL	Memory buffer
SCB7_EZ_DATA240	0x406707C0	FULL	Memory buffer
SCB7_EZ_DATA241	0x406707C4	FULL	Memory buffer
SCB7_EZ_DATA242	0x406707C8	FULL	Memory buffer
SCB7_EZ_DATA243	0x406707CC	FULL	Memory buffer
SCB7_EZ_DATA244	0x406707D0	FULL	Memory buffer
SCB7_EZ_DATA245	0x406707D4	FULL	Memory buffer
SCB7_EZ_DATA246	0x406707D8	FULL	Memory buffer
SCB7_EZ_DATA247	0x406707DC	FULL	Memory buffer
SCB7_EZ_DATA248	0x406707E0	FULL	Memory buffer
SCB7_EZ_DATA249	0x406707E4	FULL	Memory buffer
SCB7_EZ_DATA250	0x406707E8	FULL	Memory buffer
SCB7_EZ_DATA251	0x406707EC	FULL	Memory buffer
SCB7_EZ_DATA252	0x406707F0	FULL	Memory buffer
SCB7_EZ_DATA253	0x406707F4	FULL	Memory buffer
SCB7_EZ_DATA254	0x406707F8	FULL	Memory buffer
SCB7_EZ_DATA255	0x406707FC	FULL	Memory buffer
SCB7_INTR_CAUSE	0x40670E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB7_INTR_SPI_EC	0x40670EC0	FULL	Externally clocked SPI interrupt request
SCB7_INTR_SPI_EC_MASK	0x40670EC8	FULL	Externally clocked SPI interrupt mask
SCB7_INTR_SPI_EC_MASKED	0x40670ECC	FULL	Externally clocked SPI interrupt masked
SCB7_INTR_M	0x40670F00	FULL	Master interrupt request
SCB7_INTR_M_SET	0x40670F04	FULL	Master interrupt set request
SCB7_INTR_M_MASK	0x40670F08	FULL	Master interrupt mask
SCB7_INTR_M_MASKED	0x40670F0C	FULL	Master interrupt masked request
SCB7_INTR_S	0x40670F40	FULL	Slave interrupt request
SCB7_INTR_S_SET	0x40670F44	FULL	Slave interrupt set request
SCB7_INTR_S_MASK	0x40670F48	FULL	Slave interrupt mask
SCB7_INTR_S_MASKED	0x40670F4C	FULL	Slave interrupt masked request
SCB7_INTR_TX	0x40670F80	FULL	Transmitter interrupt request
SCB7_INTR_TX_SET	0x40670F84	FULL	Transmitter interrupt set request
SCB7_INTR_TX_MASK	0x40670F88	FULL	Transmitter interrupt mask
SCB7_INTR_TX_MASKED	0x40670F8C	FULL	Transmitter interrupt masked request
SCB7_INTR_RX	0x40670FC0	FULL	Receiver interrupt request
SCB7_INTR_RX_SET	0x40670FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB7_INTR_RX_MASK	0x40670FC8	FULL	Receiver interrupt mask
SCB7_INTR_RX_MASKED	0x40670FCC	FULL	Receiver interrupt masked request

24.9 SCB 8

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40680000

Size 0x10000

Slave Num MMIO6 - 8

Register Name	Address	Permission	Description
SCB8_CTRL	0x40680000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB8_STATUS	0x40680004	FULL	Generic status
SCB8_SPI_CTRL	0x40680020	FULL	SPI control
SCB8_SPI_STATUS	0x40680024	FULL	SPI status
SCB8_SPI_TX_CTRL	0x40680028	FULL	SPI transmitter control
SCB8_SPI_RX_CTRL	0x4068002C	FULL	SPI receiver control
SCB8_UART_CTRL	0x40680040	FULL	UART control
SCB8_UART_TX_CTRL	0x40680044	FULL	UART transmitter control
SCB8_UART_RX_CTRL	0x40680048	FULL	UART receiver control
SCB8_UART_RX_STATUS	0x4068004C	FULL	UART receiver status
SCB8_UART_FLOW_CTRL	0x40680050	FULL	UART flow control
SCB8_I2C_CTRL	0x40680060	FULL	I2C control
SCB8_I2C_STATUS	0x40680064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB8_I2C_M_CMD	0x40680068	FULL	I2C master command
SCB8_I2C_S_CMD	0x4068006C	FULL	I2C slave command
SCB8_I2C_CFG	0x40680070	FULL	I2C configuration
SCB8_TX_CTRL	0x40680200	FULL	Transmitter control
SCB8_TX_FIFO_CTRL	0x40680204	FULL	Transmitter FIFO control
SCB8_TX_FIFO_STATUS	0x40680208	FULL	Transmitter FIFO status
SCB8_TX_FIFO_WR	0x40680240	FULL	Transmitter FIFO write
SCB8_RX_CTRL	0x40680300	FULL	Receiver control
SCB8_RX_FIFO_CTRL	0x40680304	FULL	Receiver FIFO control
SCB8_RX_FIFO_STATUS	0x40680308	FULL	Receiver FIFO status
SCB8_RX_MATCH	0x40680310	FULL	Slave address and mask
SCB8_RX_FIFO_RD	0x40680340	FULL	Receiver FIFO read
SCB8_RX_FIFO_RD_SILENT	0x40680344	FULL	Receiver FIFO read silent
SCB8_EZ_DATA0	0x40680400	FULL	Memory buffer
SCB8_EZ_DATA1	0x40680404	FULL	Memory buffer
SCB8_EZ_DATA2	0x40680408	FULL	Memory buffer
SCB8_EZ_DATA3	0x4068040C	FULL	Memory buffer
SCB8_EZ_DATA4	0x40680410	FULL	Memory buffer
SCB8_EZ_DATA5	0x40680414	FULL	Memory buffer
SCB8_EZ_DATA6	0x40680418	FULL	Memory buffer
SCB8_EZ_DATA7	0x4068041C	FULL	Memory buffer
SCB8_EZ_DATA8	0x40680420	FULL	Memory buffer
SCB8_EZ_DATA9	0x40680424	FULL	Memory buffer
SCB8_EZ_DATA10	0x40680428	FULL	Memory buffer
SCB8_EZ_DATA11	0x4068042C	FULL	Memory buffer
SCB8_EZ_DATA12	0x40680430	FULL	Memory buffer
SCB8_EZ_DATA13	0x40680434	FULL	Memory buffer
SCB8_EZ_DATA14	0x40680438	FULL	Memory buffer
SCB8_EZ_DATA15	0x4068043C	FULL	Memory buffer
SCB8_EZ_DATA16	0x40680440	FULL	Memory buffer
SCB8_EZ_DATA17	0x40680444	FULL	Memory buffer
SCB8_EZ_DATA18	0x40680448	FULL	Memory buffer
SCB8_EZ_DATA19	0x4068044C	FULL	Memory buffer
SCB8_EZ_DATA20	0x40680450	FULL	Memory buffer
SCB8_EZ_DATA21	0x40680454	FULL	Memory buffer
SCB8_EZ_DATA22	0x40680458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB8_EZ_DATA23	0x4068045C	FULL	Memory buffer
SCB8_EZ_DATA24	0x40680460	FULL	Memory buffer
SCB8_EZ_DATA25	0x40680464	FULL	Memory buffer
SCB8_EZ_DATA26	0x40680468	FULL	Memory buffer
SCB8_EZ_DATA27	0x4068046C	FULL	Memory buffer
SCB8_EZ_DATA28	0x40680470	FULL	Memory buffer
SCB8_EZ_DATA29	0x40680474	FULL	Memory buffer
SCB8_EZ_DATA30	0x40680478	FULL	Memory buffer
SCB8_EZ_DATA31	0x4068047C	FULL	Memory buffer
SCB8_EZ_DATA32	0x40680480	FULL	Memory buffer
SCB8_EZ_DATA33	0x40680484	FULL	Memory buffer
SCB8_EZ_DATA34	0x40680488	FULL	Memory buffer
SCB8_EZ_DATA35	0x4068048C	FULL	Memory buffer
SCB8_EZ_DATA36	0x40680490	FULL	Memory buffer
SCB8_EZ_DATA37	0x40680494	FULL	Memory buffer
SCB8_EZ_DATA38	0x40680498	FULL	Memory buffer
SCB8_EZ_DATA39	0x4068049C	FULL	Memory buffer
SCB8_EZ_DATA40	0x406804A0	FULL	Memory buffer
SCB8_EZ_DATA41	0x406804A4	FULL	Memory buffer
SCB8_EZ_DATA42	0x406804A8	FULL	Memory buffer
SCB8_EZ_DATA43	0x406804AC	FULL	Memory buffer
SCB8_EZ_DATA44	0x406804B0	FULL	Memory buffer
SCB8_EZ_DATA45	0x406804B4	FULL	Memory buffer
SCB8_EZ_DATA46	0x406804B8	FULL	Memory buffer
SCB8_EZ_DATA47	0x406804BC	FULL	Memory buffer
SCB8_EZ_DATA48	0x406804C0	FULL	Memory buffer
SCB8_EZ_DATA49	0x406804C4	FULL	Memory buffer
SCB8_EZ_DATA50	0x406804C8	FULL	Memory buffer
SCB8_EZ_DATA51	0x406804CC	FULL	Memory buffer
SCB8_EZ_DATA52	0x406804D0	FULL	Memory buffer
SCB8_EZ_DATA53	0x406804D4	FULL	Memory buffer
SCB8_EZ_DATA54	0x406804D8	FULL	Memory buffer
SCB8_EZ_DATA55	0x406804DC	FULL	Memory buffer
SCB8_EZ_DATA56	0x406804E0	FULL	Memory buffer
SCB8_EZ_DATA57	0x406804E4	FULL	Memory buffer
SCB8_EZ_DATA58	0x406804E8	FULL	Memory buffer
SCB8_EZ_DATA59	0x406804EC	FULL	Memory buffer
SCB8_EZ_DATA60	0x406804F0	FULL	Memory buffer
SCB8_EZ_DATA61	0x406804F4	FULL	Memory buffer
SCB8_EZ_DATA62	0x406804F8	FULL	Memory buffer
SCB8_EZ_DATA63	0x406804FC	FULL	Memory buffer
SCB8_EZ_DATA64	0x40680500	FULL	Memory buffer
SCB8_EZ_DATA65	0x40680504	FULL	Memory buffer
SCB8_EZ_DATA66	0x40680508	FULL	Memory buffer
SCB8_EZ_DATA67	0x4068050C	FULL	Memory buffer
SCB8_EZ_DATA68	0x40680510	FULL	Memory buffer
SCB8_EZ_DATA69	0x40680514	FULL	Memory buffer
SCB8_EZ_DATA70	0x40680518	FULL	Memory buffer
SCB8_EZ_DATA71	0x4068051C	FULL	Memory buffer
SCB8_EZ_DATA72	0x40680520	FULL	Memory buffer
SCB8_EZ_DATA73	0x40680524	FULL	Memory buffer
SCB8_EZ_DATA74	0x40680528	FULL	Memory buffer
SCB8_EZ_DATA75	0x4068052C	FULL	Memory buffer
SCB8_EZ_DATA76	0x40680530	FULL	Memory buffer
SCB8_EZ_DATA77	0x40680534	FULL	Memory buffer
SCB8_EZ_DATA78	0x40680538	FULL	Memory buffer
SCB8_EZ_DATA79	0x4068053C	FULL	Memory buffer
SCB8_EZ_DATA80	0x40680540	FULL	Memory buffer
SCB8_EZ_DATA81	0x40680544	FULL	Memory buffer
SCB8_EZ_DATA82	0x40680548	FULL	Memory buffer
SCB8_EZ_DATA83	0x4068054C	FULL	Memory buffer
SCB8_EZ_DATA84	0x40680550	FULL	Memory buffer
SCB8_EZ_DATA85	0x40680554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB8_EZ_DATA86	0x40680558	FULL	Memory buffer
SCB8_EZ_DATA87	0x4068055C	FULL	Memory buffer
SCB8_EZ_DATA88	0x40680560	FULL	Memory buffer
SCB8_EZ_DATA89	0x40680564	FULL	Memory buffer
SCB8_EZ_DATA90	0x40680568	FULL	Memory buffer
SCB8_EZ_DATA91	0x4068056C	FULL	Memory buffer
SCB8_EZ_DATA92	0x40680570	FULL	Memory buffer
SCB8_EZ_DATA93	0x40680574	FULL	Memory buffer
SCB8_EZ_DATA94	0x40680578	FULL	Memory buffer
SCB8_EZ_DATA95	0x4068057C	FULL	Memory buffer
SCB8_EZ_DATA96	0x40680580	FULL	Memory buffer
SCB8_EZ_DATA97	0x40680584	FULL	Memory buffer
SCB8_EZ_DATA98	0x40680588	FULL	Memory buffer
SCB8_EZ_DATA99	0x4068058C	FULL	Memory buffer
SCB8_EZ_DATA100	0x40680590	FULL	Memory buffer
SCB8_EZ_DATA101	0x40680594	FULL	Memory buffer
SCB8_EZ_DATA102	0x40680598	FULL	Memory buffer
SCB8_EZ_DATA103	0x4068059C	FULL	Memory buffer
SCB8_EZ_DATA104	0x406805A0	FULL	Memory buffer
SCB8_EZ_DATA105	0x406805A4	FULL	Memory buffer
SCB8_EZ_DATA106	0x406805A8	FULL	Memory buffer
SCB8_EZ_DATA107	0x406805AC	FULL	Memory buffer
SCB8_EZ_DATA108	0x406805B0	FULL	Memory buffer
SCB8_EZ_DATA109	0x406805B4	FULL	Memory buffer
SCB8_EZ_DATA110	0x406805B8	FULL	Memory buffer
SCB8_EZ_DATA111	0x406805BC	FULL	Memory buffer
SCB8_EZ_DATA112	0x406805C0	FULL	Memory buffer
SCB8_EZ_DATA113	0x406805C4	FULL	Memory buffer
SCB8_EZ_DATA114	0x406805C8	FULL	Memory buffer
SCB8_EZ_DATA115	0x406805CC	FULL	Memory buffer
SCB8_EZ_DATA116	0x406805D0	FULL	Memory buffer
SCB8_EZ_DATA117	0x406805D4	FULL	Memory buffer
SCB8_EZ_DATA118	0x406805D8	FULL	Memory buffer
SCB8_EZ_DATA119	0x406805DC	FULL	Memory buffer
SCB8_EZ_DATA120	0x406805E0	FULL	Memory buffer
SCB8_EZ_DATA121	0x406805E4	FULL	Memory buffer
SCB8_EZ_DATA122	0x406805E8	FULL	Memory buffer
SCB8_EZ_DATA123	0x406805EC	FULL	Memory buffer
SCB8_EZ_DATA124	0x406805F0	FULL	Memory buffer
SCB8_EZ_DATA125	0x406805F4	FULL	Memory buffer
SCB8_EZ_DATA126	0x406805F8	FULL	Memory buffer
SCB8_EZ_DATA127	0x406805FC	FULL	Memory buffer
SCB8_EZ_DATA128	0x40680600	FULL	Memory buffer
SCB8_EZ_DATA129	0x40680604	FULL	Memory buffer
SCB8_EZ_DATA130	0x40680608	FULL	Memory buffer
SCB8_EZ_DATA131	0x4068060C	FULL	Memory buffer
SCB8_EZ_DATA132	0x40680610	FULL	Memory buffer
SCB8_EZ_DATA133	0x40680614	FULL	Memory buffer
SCB8_EZ_DATA134	0x40680618	FULL	Memory buffer
SCB8_EZ_DATA135	0x4068061C	FULL	Memory buffer
SCB8_EZ_DATA136	0x40680620	FULL	Memory buffer
SCB8_EZ_DATA137	0x40680624	FULL	Memory buffer
SCB8_EZ_DATA138	0x40680628	FULL	Memory buffer
SCB8_EZ_DATA139	0x4068062C	FULL	Memory buffer
SCB8_EZ_DATA140	0x40680630	FULL	Memory buffer
SCB8_EZ_DATA141	0x40680634	FULL	Memory buffer
SCB8_EZ_DATA142	0x40680638	FULL	Memory buffer
SCB8_EZ_DATA143	0x4068063C	FULL	Memory buffer
SCB8_EZ_DATA144	0x40680640	FULL	Memory buffer
SCB8_EZ_DATA145	0x40680644	FULL	Memory buffer
SCB8_EZ_DATA146	0x40680648	FULL	Memory buffer
SCB8_EZ_DATA147	0x4068064C	FULL	Memory buffer
SCB8_EZ_DATA148	0x40680650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB8_EZ_DATA149	0x40680654	FULL	Memory buffer
SCB8_EZ_DATA150	0x40680658	FULL	Memory buffer
SCB8_EZ_DATA151	0x4068065C	FULL	Memory buffer
SCB8_EZ_DATA152	0x40680660	FULL	Memory buffer
SCB8_EZ_DATA153	0x40680664	FULL	Memory buffer
SCB8_EZ_DATA154	0x40680668	FULL	Memory buffer
SCB8_EZ_DATA155	0x4068066C	FULL	Memory buffer
SCB8_EZ_DATA156	0x40680670	FULL	Memory buffer
SCB8_EZ_DATA157	0x40680674	FULL	Memory buffer
SCB8_EZ_DATA158	0x40680678	FULL	Memory buffer
SCB8_EZ_DATA159	0x4068067C	FULL	Memory buffer
SCB8_EZ_DATA160	0x40680680	FULL	Memory buffer
SCB8_EZ_DATA161	0x40680684	FULL	Memory buffer
SCB8_EZ_DATA162	0x40680688	FULL	Memory buffer
SCB8_EZ_DATA163	0x4068068C	FULL	Memory buffer
SCB8_EZ_DATA164	0x40680690	FULL	Memory buffer
SCB8_EZ_DATA165	0x40680694	FULL	Memory buffer
SCB8_EZ_DATA166	0x40680698	FULL	Memory buffer
SCB8_EZ_DATA167	0x4068069C	FULL	Memory buffer
SCB8_EZ_DATA168	0x406806A0	FULL	Memory buffer
SCB8_EZ_DATA169	0x406806A4	FULL	Memory buffer
SCB8_EZ_DATA170	0x406806A8	FULL	Memory buffer
SCB8_EZ_DATA171	0x406806AC	FULL	Memory buffer
SCB8_EZ_DATA172	0x406806B0	FULL	Memory buffer
SCB8_EZ_DATA173	0x406806B4	FULL	Memory buffer
SCB8_EZ_DATA174	0x406806B8	FULL	Memory buffer
SCB8_EZ_DATA175	0x406806BC	FULL	Memory buffer
SCB8_EZ_DATA176	0x406806C0	FULL	Memory buffer
SCB8_EZ_DATA177	0x406806C4	FULL	Memory buffer
SCB8_EZ_DATA178	0x406806C8	FULL	Memory buffer
SCB8_EZ_DATA179	0x406806CC	FULL	Memory buffer
SCB8_EZ_DATA180	0x406806D0	FULL	Memory buffer
SCB8_EZ_DATA181	0x406806D4	FULL	Memory buffer
SCB8_EZ_DATA182	0x406806D8	FULL	Memory buffer
SCB8_EZ_DATA183	0x406806DC	FULL	Memory buffer
SCB8_EZ_DATA184	0x406806E0	FULL	Memory buffer
SCB8_EZ_DATA185	0x406806E4	FULL	Memory buffer
SCB8_EZ_DATA186	0x406806E8	FULL	Memory buffer
SCB8_EZ_DATA187	0x406806EC	FULL	Memory buffer
SCB8_EZ_DATA188	0x406806F0	FULL	Memory buffer
SCB8_EZ_DATA189	0x406806F4	FULL	Memory buffer
SCB8_EZ_DATA190	0x406806F8	FULL	Memory buffer
SCB8_EZ_DATA191	0x406806FC	FULL	Memory buffer
SCB8_EZ_DATA192	0x40680700	FULL	Memory buffer
SCB8_EZ_DATA193	0x40680704	FULL	Memory buffer
SCB8_EZ_DATA194	0x40680708	FULL	Memory buffer
SCB8_EZ_DATA195	0x4068070C	FULL	Memory buffer
SCB8_EZ_DATA196	0x40680710	FULL	Memory buffer
SCB8_EZ_DATA197	0x40680714	FULL	Memory buffer
SCB8_EZ_DATA198	0x40680718	FULL	Memory buffer
SCB8_EZ_DATA199	0x4068071C	FULL	Memory buffer
SCB8_EZ_DATA200	0x40680720	FULL	Memory buffer
SCB8_EZ_DATA201	0x40680724	FULL	Memory buffer
SCB8_EZ_DATA202	0x40680728	FULL	Memory buffer
SCB8_EZ_DATA203	0x4068072C	FULL	Memory buffer
SCB8_EZ_DATA204	0x40680730	FULL	Memory buffer
SCB8_EZ_DATA205	0x40680734	FULL	Memory buffer
SCB8_EZ_DATA206	0x40680738	FULL	Memory buffer
SCB8_EZ_DATA207	0x4068073C	FULL	Memory buffer
SCB8_EZ_DATA208	0x40680740	FULL	Memory buffer
SCB8_EZ_DATA209	0x40680744	FULL	Memory buffer
SCB8_EZ_DATA210	0x40680748	FULL	Memory buffer
SCB8_EZ_DATA211	0x4068074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB8_EZ_DATA212	0x40680750	FULL	Memory buffer
SCB8_EZ_DATA213	0x40680754	FULL	Memory buffer
SCB8_EZ_DATA214	0x40680758	FULL	Memory buffer
SCB8_EZ_DATA215	0x4068075C	FULL	Memory buffer
SCB8_EZ_DATA216	0x40680760	FULL	Memory buffer
SCB8_EZ_DATA217	0x40680764	FULL	Memory buffer
SCB8_EZ_DATA218	0x40680768	FULL	Memory buffer
SCB8_EZ_DATA219	0x4068076C	FULL	Memory buffer
SCB8_EZ_DATA220	0x40680770	FULL	Memory buffer
SCB8_EZ_DATA221	0x40680774	FULL	Memory buffer
SCB8_EZ_DATA222	0x40680778	FULL	Memory buffer
SCB8_EZ_DATA223	0x4068077C	FULL	Memory buffer
SCB8_EZ_DATA224	0x40680780	FULL	Memory buffer
SCB8_EZ_DATA225	0x40680784	FULL	Memory buffer
SCB8_EZ_DATA226	0x40680788	FULL	Memory buffer
SCB8_EZ_DATA227	0x4068078C	FULL	Memory buffer
SCB8_EZ_DATA228	0x40680790	FULL	Memory buffer
SCB8_EZ_DATA229	0x40680794	FULL	Memory buffer
SCB8_EZ_DATA230	0x40680798	FULL	Memory buffer
SCB8_EZ_DATA231	0x4068079C	FULL	Memory buffer
SCB8_EZ_DATA232	0x406807A0	FULL	Memory buffer
SCB8_EZ_DATA233	0x406807A4	FULL	Memory buffer
SCB8_EZ_DATA234	0x406807A8	FULL	Memory buffer
SCB8_EZ_DATA235	0x406807AC	FULL	Memory buffer
SCB8_EZ_DATA236	0x406807B0	FULL	Memory buffer
SCB8_EZ_DATA237	0x406807B4	FULL	Memory buffer
SCB8_EZ_DATA238	0x406807B8	FULL	Memory buffer
SCB8_EZ_DATA239	0x406807BC	FULL	Memory buffer
SCB8_EZ_DATA240	0x406807C0	FULL	Memory buffer
SCB8_EZ_DATA241	0x406807C4	FULL	Memory buffer
SCB8_EZ_DATA242	0x406807C8	FULL	Memory buffer
SCB8_EZ_DATA243	0x406807CC	FULL	Memory buffer
SCB8_EZ_DATA244	0x406807D0	FULL	Memory buffer
SCB8_EZ_DATA245	0x406807D4	FULL	Memory buffer
SCB8_EZ_DATA246	0x406807D8	FULL	Memory buffer
SCB8_EZ_DATA247	0x406807DC	FULL	Memory buffer
SCB8_EZ_DATA248	0x406807E0	FULL	Memory buffer
SCB8_EZ_DATA249	0x406807E4	FULL	Memory buffer
SCB8_EZ_DATA250	0x406807E8	FULL	Memory buffer
SCB8_EZ_DATA251	0x406807EC	FULL	Memory buffer
SCB8_EZ_DATA252	0x406807F0	FULL	Memory buffer
SCB8_EZ_DATA253	0x406807F4	FULL	Memory buffer
SCB8_EZ_DATA254	0x406807F8	FULL	Memory buffer
SCB8_EZ_DATA255	0x406807FC	FULL	Memory buffer
SCB8_INTR_CAUSE	0x40680E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB8_INTR_SPI_EC	0x40680EC0	FULL	Externally clocked SPI interrupt request
SCB8_INTR_SPI_EC_MASK	0x40680EC8	FULL	Externally clocked SPI interrupt mask
SCB8_INTR_SPI_EC_MASKED	0x40680ECC	FULL	Externally clocked SPI interrupt masked
SCB8_INTR_M	0x40680F00	FULL	Master interrupt request
SCB8_INTR_M_SET	0x40680F04	FULL	Master interrupt set request
SCB8_INTR_M_MASK	0x40680F08	FULL	Master interrupt mask
SCB8_INTR_M_MASKED	0x40680F0C	FULL	Master interrupt masked request
SCB8_INTR_S	0x40680F40	FULL	Slave interrupt request
SCB8_INTR_S_SET	0x40680F44	FULL	Slave interrupt set request
SCB8_INTR_S_MASK	0x40680F48	FULL	Slave interrupt mask
SCB8_INTR_S_MASKED	0x40680F4C	FULL	Slave interrupt masked request
SCB8_INTR_TX	0x40680F80	FULL	Transmitter interrupt request
SCB8_INTR_TX_SET	0x40680F84	FULL	Transmitter interrupt set request
SCB8_INTR_TX_MASK	0x40680F88	FULL	Transmitter interrupt mask
SCB8_INTR_TX_MASKED	0x40680F8C	FULL	Transmitter interrupt masked request
SCB8_INTR_RX	0x40680FC0	FULL	Receiver interrupt request
SCB8_INTR_RX_SET	0x40680FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB8_INTR_RX_MASK	0x40680FC8	FULL	Receiver interrupt mask
SCB8_INTR_RX_MASKED	0x40680FCC	FULL	Receiver interrupt masked request

24.10 SCB 9

Description Serial Communications Block
(SPI/UART/I2C)

Base Address 0x40690000

Size 0x10000

Slave Num MMIO6 - 9

Register Name	Address	Permission	Description
SCB9_CTRL	0x40690000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB9_STATUS	0x40690004	FULL	Generic status
SCB9_SPI_CTRL	0x40690020	FULL	SPI control
SCB9_SPI_STATUS	0x40690024	FULL	SPI status
SCB9_SPI_TX_CTRL	0x40690028	FULL	SPI transmitter control
SCB9_SPI_RX_CTRL	0x4069002C	FULL	SPI receiver control
SCB9_UART_CTRL	0x40690040	FULL	UART control
SCB9_UART_TX_CTRL	0x40690044	FULL	UART transmitter control
SCB9_UART_RX_CTRL	0x40690048	FULL	UART receiver control
SCB9_UART_RX_STATUS	0x4069004C	FULL	UART receiver status
SCB9_UART_FLOW_CTRL	0x40690050	FULL	UART flow control
SCB9_I2C_CTRL	0x40690060	FULL	I2C control
SCB9_I2C_STATUS	0x40690064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB9_I2C_M_CMD	0x40690068	FULL	I2C master command
SCB9_I2C_S_CMD	0x4069006C	FULL	I2C slave command
SCB9_I2C_CFG	0x40690070	FULL	I2C configuration
SCB9_TX_CTRL	0x40690200	FULL	Transmitter control
SCB9_TX_FIFO_CTRL	0x40690204	FULL	Transmitter FIFO control
SCB9_TX_FIFO_STATUS	0x40690208	FULL	Transmitter FIFO status
SCB9_TX_FIFO_WR	0x40690240	FULL	Transmitter FIFO write
SCB9_RX_CTRL	0x40690300	FULL	Receiver control
SCB9_RX_FIFO_CTRL	0x40690304	FULL	Receiver FIFO control
SCB9_RX_FIFO_STATUS	0x40690308	FULL	Receiver FIFO status
SCB9_RX_MATCH	0x40690310	FULL	Slave address and mask
SCB9_RX_FIFO_RD	0x40690340	FULL	Receiver FIFO read
SCB9_RX_FIFO_RD_SILENT	0x40690344	FULL	Receiver FIFO read silent
SCB9_EZ_DATA0	0x40690400	FULL	Memory buffer
SCB9_EZ_DATA1	0x40690404	FULL	Memory buffer
SCB9_EZ_DATA2	0x40690408	FULL	Memory buffer
SCB9_EZ_DATA3	0x4069040C	FULL	Memory buffer
SCB9_EZ_DATA4	0x40690410	FULL	Memory buffer
SCB9_EZ_DATA5	0x40690414	FULL	Memory buffer
SCB9_EZ_DATA6	0x40690418	FULL	Memory buffer
SCB9_EZ_DATA7	0x4069041C	FULL	Memory buffer
SCB9_EZ_DATA8	0x40690420	FULL	Memory buffer
SCB9_EZ_DATA9	0x40690424	FULL	Memory buffer
SCB9_EZ_DATA10	0x40690428	FULL	Memory buffer
SCB9_EZ_DATA11	0x4069042C	FULL	Memory buffer
SCB9_EZ_DATA12	0x40690430	FULL	Memory buffer
SCB9_EZ_DATA13	0x40690434	FULL	Memory buffer
SCB9_EZ_DATA14	0x40690438	FULL	Memory buffer
SCB9_EZ_DATA15	0x4069043C	FULL	Memory buffer
SCB9_EZ_DATA16	0x40690440	FULL	Memory buffer
SCB9_EZ_DATA17	0x40690444	FULL	Memory buffer
SCB9_EZ_DATA18	0x40690448	FULL	Memory buffer
SCB9_EZ_DATA19	0x4069044C	FULL	Memory buffer
SCB9_EZ_DATA20	0x40690450	FULL	Memory buffer
SCB9_EZ_DATA21	0x40690454	FULL	Memory buffer
SCB9_EZ_DATA22	0x40690458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB9_EZ_DATA23	0x4069045C	FULL	Memory buffer
SCB9_EZ_DATA24	0x40690460	FULL	Memory buffer
SCB9_EZ_DATA25	0x40690464	FULL	Memory buffer
SCB9_EZ_DATA26	0x40690468	FULL	Memory buffer
SCB9_EZ_DATA27	0x4069046C	FULL	Memory buffer
SCB9_EZ_DATA28	0x40690470	FULL	Memory buffer
SCB9_EZ_DATA29	0x40690474	FULL	Memory buffer
SCB9_EZ_DATA30	0x40690478	FULL	Memory buffer
SCB9_EZ_DATA31	0x4069047C	FULL	Memory buffer
SCB9_EZ_DATA32	0x40690480	FULL	Memory buffer
SCB9_EZ_DATA33	0x40690484	FULL	Memory buffer
SCB9_EZ_DATA34	0x40690488	FULL	Memory buffer
SCB9_EZ_DATA35	0x4069048C	FULL	Memory buffer
SCB9_EZ_DATA36	0x40690490	FULL	Memory buffer
SCB9_EZ_DATA37	0x40690494	FULL	Memory buffer
SCB9_EZ_DATA38	0x40690498	FULL	Memory buffer
SCB9_EZ_DATA39	0x4069049C	FULL	Memory buffer
SCB9_EZ_DATA40	0x406904A0	FULL	Memory buffer
SCB9_EZ_DATA41	0x406904A4	FULL	Memory buffer
SCB9_EZ_DATA42	0x406904A8	FULL	Memory buffer
SCB9_EZ_DATA43	0x406904AC	FULL	Memory buffer
SCB9_EZ_DATA44	0x406904B0	FULL	Memory buffer
SCB9_EZ_DATA45	0x406904B4	FULL	Memory buffer
SCB9_EZ_DATA46	0x406904B8	FULL	Memory buffer
SCB9_EZ_DATA47	0x406904BC	FULL	Memory buffer
SCB9_EZ_DATA48	0x406904C0	FULL	Memory buffer
SCB9_EZ_DATA49	0x406904C4	FULL	Memory buffer
SCB9_EZ_DATA50	0x406904C8	FULL	Memory buffer
SCB9_EZ_DATA51	0x406904CC	FULL	Memory buffer
SCB9_EZ_DATA52	0x406904D0	FULL	Memory buffer
SCB9_EZ_DATA53	0x406904D4	FULL	Memory buffer
SCB9_EZ_DATA54	0x406904D8	FULL	Memory buffer
SCB9_EZ_DATA55	0x406904DC	FULL	Memory buffer
SCB9_EZ_DATA56	0x406904E0	FULL	Memory buffer
SCB9_EZ_DATA57	0x406904E4	FULL	Memory buffer
SCB9_EZ_DATA58	0x406904E8	FULL	Memory buffer
SCB9_EZ_DATA59	0x406904EC	FULL	Memory buffer
SCB9_EZ_DATA60	0x406904F0	FULL	Memory buffer
SCB9_EZ_DATA61	0x406904F4	FULL	Memory buffer
SCB9_EZ_DATA62	0x406904F8	FULL	Memory buffer
SCB9_EZ_DATA63	0x406904FC	FULL	Memory buffer
SCB9_EZ_DATA64	0x40690500	FULL	Memory buffer
SCB9_EZ_DATA65	0x40690504	FULL	Memory buffer
SCB9_EZ_DATA66	0x40690508	FULL	Memory buffer
SCB9_EZ_DATA67	0x4069050C	FULL	Memory buffer
SCB9_EZ_DATA68	0x40690510	FULL	Memory buffer
SCB9_EZ_DATA69	0x40690514	FULL	Memory buffer
SCB9_EZ_DATA70	0x40690518	FULL	Memory buffer
SCB9_EZ_DATA71	0x4069051C	FULL	Memory buffer
SCB9_EZ_DATA72	0x40690520	FULL	Memory buffer
SCB9_EZ_DATA73	0x40690524	FULL	Memory buffer
SCB9_EZ_DATA74	0x40690528	FULL	Memory buffer
SCB9_EZ_DATA75	0x4069052C	FULL	Memory buffer
SCB9_EZ_DATA76	0x40690530	FULL	Memory buffer
SCB9_EZ_DATA77	0x40690534	FULL	Memory buffer
SCB9_EZ_DATA78	0x40690538	FULL	Memory buffer
SCB9_EZ_DATA79	0x4069053C	FULL	Memory buffer
SCB9_EZ_DATA80	0x40690540	FULL	Memory buffer
SCB9_EZ_DATA81	0x40690544	FULL	Memory buffer
SCB9_EZ_DATA82	0x40690548	FULL	Memory buffer
SCB9_EZ_DATA83	0x4069054C	FULL	Memory buffer
SCB9_EZ_DATA84	0x40690550	FULL	Memory buffer
SCB9_EZ_DATA85	0x40690554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB9_EZ_DATA86	0x40690558	FULL	Memory buffer
SCB9_EZ_DATA87	0x4069055C	FULL	Memory buffer
SCB9_EZ_DATA88	0x40690560	FULL	Memory buffer
SCB9_EZ_DATA89	0x40690564	FULL	Memory buffer
SCB9_EZ_DATA90	0x40690568	FULL	Memory buffer
SCB9_EZ_DATA91	0x4069056C	FULL	Memory buffer
SCB9_EZ_DATA92	0x40690570	FULL	Memory buffer
SCB9_EZ_DATA93	0x40690574	FULL	Memory buffer
SCB9_EZ_DATA94	0x40690578	FULL	Memory buffer
SCB9_EZ_DATA95	0x4069057C	FULL	Memory buffer
SCB9_EZ_DATA96	0x40690580	FULL	Memory buffer
SCB9_EZ_DATA97	0x40690584	FULL	Memory buffer
SCB9_EZ_DATA98	0x40690588	FULL	Memory buffer
SCB9_EZ_DATA99	0x4069058C	FULL	Memory buffer
SCB9_EZ_DATA100	0x40690590	FULL	Memory buffer
SCB9_EZ_DATA101	0x40690594	FULL	Memory buffer
SCB9_EZ_DATA102	0x40690598	FULL	Memory buffer
SCB9_EZ_DATA103	0x4069059C	FULL	Memory buffer
SCB9_EZ_DATA104	0x406905A0	FULL	Memory buffer
SCB9_EZ_DATA105	0x406905A4	FULL	Memory buffer
SCB9_EZ_DATA106	0x406905A8	FULL	Memory buffer
SCB9_EZ_DATA107	0x406905AC	FULL	Memory buffer
SCB9_EZ_DATA108	0x406905B0	FULL	Memory buffer
SCB9_EZ_DATA109	0x406905B4	FULL	Memory buffer
SCB9_EZ_DATA110	0x406905B8	FULL	Memory buffer
SCB9_EZ_DATA111	0x406905BC	FULL	Memory buffer
SCB9_EZ_DATA112	0x406905C0	FULL	Memory buffer
SCB9_EZ_DATA113	0x406905C4	FULL	Memory buffer
SCB9_EZ_DATA114	0x406905C8	FULL	Memory buffer
SCB9_EZ_DATA115	0x406905CC	FULL	Memory buffer
SCB9_EZ_DATA116	0x406905D0	FULL	Memory buffer
SCB9_EZ_DATA117	0x406905D4	FULL	Memory buffer
SCB9_EZ_DATA118	0x406905D8	FULL	Memory buffer
SCB9_EZ_DATA119	0x406905DC	FULL	Memory buffer
SCB9_EZ_DATA120	0x406905E0	FULL	Memory buffer
SCB9_EZ_DATA121	0x406905E4	FULL	Memory buffer
SCB9_EZ_DATA122	0x406905E8	FULL	Memory buffer
SCB9_EZ_DATA123	0x406905EC	FULL	Memory buffer
SCB9_EZ_DATA124	0x406905F0	FULL	Memory buffer
SCB9_EZ_DATA125	0x406905F4	FULL	Memory buffer
SCB9_EZ_DATA126	0x406905F8	FULL	Memory buffer
SCB9_EZ_DATA127	0x406905FC	FULL	Memory buffer
SCB9_EZ_DATA128	0x40690600	FULL	Memory buffer
SCB9_EZ_DATA129	0x40690604	FULL	Memory buffer
SCB9_EZ_DATA130	0x40690608	FULL	Memory buffer
SCB9_EZ_DATA131	0x4069060C	FULL	Memory buffer
SCB9_EZ_DATA132	0x40690610	FULL	Memory buffer
SCB9_EZ_DATA133	0x40690614	FULL	Memory buffer
SCB9_EZ_DATA134	0x40690618	FULL	Memory buffer
SCB9_EZ_DATA135	0x4069061C	FULL	Memory buffer
SCB9_EZ_DATA136	0x40690620	FULL	Memory buffer
SCB9_EZ_DATA137	0x40690624	FULL	Memory buffer
SCB9_EZ_DATA138	0x40690628	FULL	Memory buffer
SCB9_EZ_DATA139	0x4069062C	FULL	Memory buffer
SCB9_EZ_DATA140	0x40690630	FULL	Memory buffer
SCB9_EZ_DATA141	0x40690634	FULL	Memory buffer
SCB9_EZ_DATA142	0x40690638	FULL	Memory buffer
SCB9_EZ_DATA143	0x4069063C	FULL	Memory buffer
SCB9_EZ_DATA144	0x40690640	FULL	Memory buffer
SCB9_EZ_DATA145	0x40690644	FULL	Memory buffer
SCB9_EZ_DATA146	0x40690648	FULL	Memory buffer
SCB9_EZ_DATA147	0x4069064C	FULL	Memory buffer
SCB9_EZ_DATA148	0x40690650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB9_EZ_DATA149	0x40690654	FULL	Memory buffer
SCB9_EZ_DATA150	0x40690658	FULL	Memory buffer
SCB9_EZ_DATA151	0x4069065C	FULL	Memory buffer
SCB9_EZ_DATA152	0x40690660	FULL	Memory buffer
SCB9_EZ_DATA153	0x40690664	FULL	Memory buffer
SCB9_EZ_DATA154	0x40690668	FULL	Memory buffer
SCB9_EZ_DATA155	0x4069066C	FULL	Memory buffer
SCB9_EZ_DATA156	0x40690670	FULL	Memory buffer
SCB9_EZ_DATA157	0x40690674	FULL	Memory buffer
SCB9_EZ_DATA158	0x40690678	FULL	Memory buffer
SCB9_EZ_DATA159	0x4069067C	FULL	Memory buffer
SCB9_EZ_DATA160	0x40690680	FULL	Memory buffer
SCB9_EZ_DATA161	0x40690684	FULL	Memory buffer
SCB9_EZ_DATA162	0x40690688	FULL	Memory buffer
SCB9_EZ_DATA163	0x4069068C	FULL	Memory buffer
SCB9_EZ_DATA164	0x40690690	FULL	Memory buffer
SCB9_EZ_DATA165	0x40690694	FULL	Memory buffer
SCB9_EZ_DATA166	0x40690698	FULL	Memory buffer
SCB9_EZ_DATA167	0x4069069C	FULL	Memory buffer
SCB9_EZ_DATA168	0x406906A0	FULL	Memory buffer
SCB9_EZ_DATA169	0x406906A4	FULL	Memory buffer
SCB9_EZ_DATA170	0x406906A8	FULL	Memory buffer
SCB9_EZ_DATA171	0x406906AC	FULL	Memory buffer
SCB9_EZ_DATA172	0x406906B0	FULL	Memory buffer
SCB9_EZ_DATA173	0x406906B4	FULL	Memory buffer
SCB9_EZ_DATA174	0x406906B8	FULL	Memory buffer
SCB9_EZ_DATA175	0x406906BC	FULL	Memory buffer
SCB9_EZ_DATA176	0x406906C0	FULL	Memory buffer
SCB9_EZ_DATA177	0x406906C4	FULL	Memory buffer
SCB9_EZ_DATA178	0x406906C8	FULL	Memory buffer
SCB9_EZ_DATA179	0x406906CC	FULL	Memory buffer
SCB9_EZ_DATA180	0x406906D0	FULL	Memory buffer
SCB9_EZ_DATA181	0x406906D4	FULL	Memory buffer
SCB9_EZ_DATA182	0x406906D8	FULL	Memory buffer
SCB9_EZ_DATA183	0x406906DC	FULL	Memory buffer
SCB9_EZ_DATA184	0x406906E0	FULL	Memory buffer
SCB9_EZ_DATA185	0x406906E4	FULL	Memory buffer
SCB9_EZ_DATA186	0x406906E8	FULL	Memory buffer
SCB9_EZ_DATA187	0x406906EC	FULL	Memory buffer
SCB9_EZ_DATA188	0x406906F0	FULL	Memory buffer
SCB9_EZ_DATA189	0x406906F4	FULL	Memory buffer
SCB9_EZ_DATA190	0x406906F8	FULL	Memory buffer
SCB9_EZ_DATA191	0x406906FC	FULL	Memory buffer
SCB9_EZ_DATA192	0x40690700	FULL	Memory buffer
SCB9_EZ_DATA193	0x40690704	FULL	Memory buffer
SCB9_EZ_DATA194	0x40690708	FULL	Memory buffer
SCB9_EZ_DATA195	0x4069070C	FULL	Memory buffer
SCB9_EZ_DATA196	0x40690710	FULL	Memory buffer
SCB9_EZ_DATA197	0x40690714	FULL	Memory buffer
SCB9_EZ_DATA198	0x40690718	FULL	Memory buffer
SCB9_EZ_DATA199	0x4069071C	FULL	Memory buffer
SCB9_EZ_DATA200	0x40690720	FULL	Memory buffer
SCB9_EZ_DATA201	0x40690724	FULL	Memory buffer
SCB9_EZ_DATA202	0x40690728	FULL	Memory buffer
SCB9_EZ_DATA203	0x4069072C	FULL	Memory buffer
SCB9_EZ_DATA204	0x40690730	FULL	Memory buffer
SCB9_EZ_DATA205	0x40690734	FULL	Memory buffer
SCB9_EZ_DATA206	0x40690738	FULL	Memory buffer
SCB9_EZ_DATA207	0x4069073C	FULL	Memory buffer
SCB9_EZ_DATA208	0x40690740	FULL	Memory buffer
SCB9_EZ_DATA209	0x40690744	FULL	Memory buffer
SCB9_EZ_DATA210	0x40690748	FULL	Memory buffer
SCB9_EZ_DATA211	0x4069074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB9_EZ_DATA212	0x40690750	FULL	Memory buffer
SCB9_EZ_DATA213	0x40690754	FULL	Memory buffer
SCB9_EZ_DATA214	0x40690758	FULL	Memory buffer
SCB9_EZ_DATA215	0x4069075C	FULL	Memory buffer
SCB9_EZ_DATA216	0x40690760	FULL	Memory buffer
SCB9_EZ_DATA217	0x40690764	FULL	Memory buffer
SCB9_EZ_DATA218	0x40690768	FULL	Memory buffer
SCB9_EZ_DATA219	0x4069076C	FULL	Memory buffer
SCB9_EZ_DATA220	0x40690770	FULL	Memory buffer
SCB9_EZ_DATA221	0x40690774	FULL	Memory buffer
SCB9_EZ_DATA222	0x40690778	FULL	Memory buffer
SCB9_EZ_DATA223	0x4069077C	FULL	Memory buffer
SCB9_EZ_DATA224	0x40690780	FULL	Memory buffer
SCB9_EZ_DATA225	0x40690784	FULL	Memory buffer
SCB9_EZ_DATA226	0x40690788	FULL	Memory buffer
SCB9_EZ_DATA227	0x4069078C	FULL	Memory buffer
SCB9_EZ_DATA228	0x40690790	FULL	Memory buffer
SCB9_EZ_DATA229	0x40690794	FULL	Memory buffer
SCB9_EZ_DATA230	0x40690798	FULL	Memory buffer
SCB9_EZ_DATA231	0x4069079C	FULL	Memory buffer
SCB9_EZ_DATA232	0x406907A0	FULL	Memory buffer
SCB9_EZ_DATA233	0x406907A4	FULL	Memory buffer
SCB9_EZ_DATA234	0x406907A8	FULL	Memory buffer
SCB9_EZ_DATA235	0x406907AC	FULL	Memory buffer
SCB9_EZ_DATA236	0x406907B0	FULL	Memory buffer
SCB9_EZ_DATA237	0x406907B4	FULL	Memory buffer
SCB9_EZ_DATA238	0x406907B8	FULL	Memory buffer
SCB9_EZ_DATA239	0x406907BC	FULL	Memory buffer
SCB9_EZ_DATA240	0x406907C0	FULL	Memory buffer
SCB9_EZ_DATA241	0x406907C4	FULL	Memory buffer
SCB9_EZ_DATA242	0x406907C8	FULL	Memory buffer
SCB9_EZ_DATA243	0x406907CC	FULL	Memory buffer
SCB9_EZ_DATA244	0x406907D0	FULL	Memory buffer
SCB9_EZ_DATA245	0x406907D4	FULL	Memory buffer
SCB9_EZ_DATA246	0x406907D8	FULL	Memory buffer
SCB9_EZ_DATA247	0x406907DC	FULL	Memory buffer
SCB9_EZ_DATA248	0x406907E0	FULL	Memory buffer
SCB9_EZ_DATA249	0x406907E4	FULL	Memory buffer
SCB9_EZ_DATA250	0x406907E8	FULL	Memory buffer
SCB9_EZ_DATA251	0x406907EC	FULL	Memory buffer
SCB9_EZ_DATA252	0x406907F0	FULL	Memory buffer
SCB9_EZ_DATA253	0x406907F4	FULL	Memory buffer
SCB9_EZ_DATA254	0x406907F8	FULL	Memory buffer
SCB9_EZ_DATA255	0x406907FC	FULL	Memory buffer
SCB9_INTR_CAUSE	0x40690E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB9_INTR_SPI_EC	0x40690EC0	FULL	Externally clocked SPI interrupt request
SCB9_INTR_SPI_EC_MASK	0x40690EC8	FULL	Externally clocked SPI interrupt mask
SCB9_INTR_SPI_EC_MASKED	0x40690ECC	FULL	Externally clocked SPI interrupt masked
SCB9_INTR_M	0x40690F00	FULL	Master interrupt request
SCB9_INTR_M_SET	0x40690F04	FULL	Master interrupt set request
SCB9_INTR_M_MASK	0x40690F08	FULL	Master interrupt mask
SCB9_INTR_M_MASKED	0x40690F0C	FULL	Master interrupt masked request
SCB9_INTR_S	0x40690F40	FULL	Slave interrupt request
SCB9_INTR_S_SET	0x40690F44	FULL	Slave interrupt set request
SCB9_INTR_S_MASK	0x40690F48	FULL	Slave interrupt mask
SCB9_INTR_S_MASKED	0x40690F4C	FULL	Slave interrupt masked request
SCB9_INTR_TX	0x40690F80	FULL	Transmitter interrupt request
SCB9_INTR_TX_SET	0x40690F84	FULL	Transmitter interrupt set request
SCB9_INTR_TX_MASK	0x40690F88	FULL	Transmitter interrupt mask
SCB9_INTR_TX_MASKED	0x40690F8C	FULL	Transmitter interrupt masked request
SCB9_INTR_RX	0x40690FC0	FULL	Receiver interrupt request
SCB9_INTR_RX_SET	0x40690FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB9_INTR_RX_MASK	0x40690FC8	FULL	Receiver interrupt mask
SCB9_INTR_RX_MASKED	0x40690FCC	FULL	Receiver interrupt masked request

24.11 SCB 10

Description Serial Communications Block
(SPI/UART/I2C)
Base Address 0x406A0000
Size 0x10000
Slave Num MMIO6 - 10

Register Name	Address	Permission	Description
SCB10_CTRL	0x406A0000	FULL	Generic control Note: CMD_RESP_MODE is not available for this register
SCB10_STATUS	0x406A0004	FULL	Generic status
SCB10_SPI_CTRL	0x406A0020	FULL	SPI control
SCB10_SPI_STATUS	0x406A0024	FULL	SPI status
SCB10_SPI_TX_CTRL	0x406A0028	FULL	SPI transmitter control
SCB10_SPI_RX_CTRL	0x406A002C	FULL	SPI receiver control
SCB10_UART_CTRL	0x406A0040	FULL	UART control
SCB10_UART_TX_CTRL	0x406A0044	FULL	UART transmitter control
SCB10_UART_RX_CTRL	0x406A0048	FULL	UART receiver control
SCB10_UART_RX_STATUS	0x406A004C	FULL	UART receiver status
SCB10_UART_FLOW_CTRL	0x406A0050	FULL	UART flow control
SCB10_I2C_CTRL	0x406A0060	FULL	I2C control
SCB10_I2C_STATUS	0x406A0064	FULL	I2C status Note: I2C_EC_BUSY is not available for this register
SCB10_I2C_M_CMD	0x406A0068	FULL	I2C master command
SCB10_I2C_S_CMD	0x406A006C	FULL	I2C slave command
SCB10_I2C_CFG	0x406A0070	FULL	I2C configuration
SCB10_TX_CTRL	0x406A0200	FULL	Transmitter control
SCB10_TX_FIFO_CTRL	0x406A0204	FULL	Transmitter FIFO control
SCB10_TX_FIFO_STATUS	0x406A0208	FULL	Transmitter FIFO status
SCB10_TX_FIFO_WR	0x406A0240	FULL	Transmitter FIFO write
SCB10_RX_CTRL	0x406A0300	FULL	Receiver control
SCB10_RX_FIFO_CTRL	0x406A0304	FULL	Receiver FIFO control
SCB10_RX_FIFO_STATUS	0x406A0308	FULL	Receiver FIFO status
SCB10_RX_MATCH	0x406A0310	FULL	Slave address and mask
SCB10_RX_FIFO_RD	0x406A0340	FULL	Receiver FIFO read
SCB10_RX_FIFO_RD_SILENT	0x406A0344	FULL	Receiver FIFO read silent
SCB10_EZ_DATA0	0x406A0400	FULL	Memory buffer
SCB10_EZ_DATA1	0x406A0404	FULL	Memory buffer
SCB10_EZ_DATA2	0x406A0408	FULL	Memory buffer
SCB10_EZ_DATA3	0x406A040C	FULL	Memory buffer
SCB10_EZ_DATA4	0x406A0410	FULL	Memory buffer
SCB10_EZ_DATA5	0x406A0414	FULL	Memory buffer
SCB10_EZ_DATA6	0x406A0418	FULL	Memory buffer
SCB10_EZ_DATA7	0x406A041C	FULL	Memory buffer
SCB10_EZ_DATA8	0x406A0420	FULL	Memory buffer
SCB10_EZ_DATA9	0x406A0424	FULL	Memory buffer
SCB10_EZ_DATA10	0x406A0428	FULL	Memory buffer
SCB10_EZ_DATA11	0x406A042C	FULL	Memory buffer
SCB10_EZ_DATA12	0x406A0430	FULL	Memory buffer
SCB10_EZ_DATA13	0x406A0434	FULL	Memory buffer
SCB10_EZ_DATA14	0x406A0438	FULL	Memory buffer
SCB10_EZ_DATA15	0x406A043C	FULL	Memory buffer
SCB10_EZ_DATA16	0x406A0440	FULL	Memory buffer
SCB10_EZ_DATA17	0x406A0444	FULL	Memory buffer
SCB10_EZ_DATA18	0x406A0448	FULL	Memory buffer
SCB10_EZ_DATA19	0x406A044C	FULL	Memory buffer
SCB10_EZ_DATA20	0x406A0450	FULL	Memory buffer
SCB10_EZ_DATA21	0x406A0454	FULL	Memory buffer
SCB10_EZ_DATA22	0x406A0458	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB10_EZ_DATA23	0x406A045C	FULL	Memory buffer
SCB10_EZ_DATA24	0x406A0460	FULL	Memory buffer
SCB10_EZ_DATA25	0x406A0464	FULL	Memory buffer
SCB10_EZ_DATA26	0x406A0468	FULL	Memory buffer
SCB10_EZ_DATA27	0x406A046C	FULL	Memory buffer
SCB10_EZ_DATA28	0x406A0470	FULL	Memory buffer
SCB10_EZ_DATA29	0x406A0474	FULL	Memory buffer
SCB10_EZ_DATA30	0x406A0478	FULL	Memory buffer
SCB10_EZ_DATA31	0x406A047C	FULL	Memory buffer
SCB10_EZ_DATA32	0x406A0480	FULL	Memory buffer
SCB10_EZ_DATA33	0x406A0484	FULL	Memory buffer
SCB10_EZ_DATA34	0x406A0488	FULL	Memory buffer
SCB10_EZ_DATA35	0x406A048C	FULL	Memory buffer
SCB10_EZ_DATA36	0x406A0490	FULL	Memory buffer
SCB10_EZ_DATA37	0x406A0494	FULL	Memory buffer
SCB10_EZ_DATA38	0x406A0498	FULL	Memory buffer
SCB10_EZ_DATA39	0x406A049C	FULL	Memory buffer
SCB10_EZ_DATA40	0x406A04A0	FULL	Memory buffer
SCB10_EZ_DATA41	0x406A04A4	FULL	Memory buffer
SCB10_EZ_DATA42	0x406A04A8	FULL	Memory buffer
SCB10_EZ_DATA43	0x406A04AC	FULL	Memory buffer
SCB10_EZ_DATA44	0x406A04B0	FULL	Memory buffer
SCB10_EZ_DATA45	0x406A04B4	FULL	Memory buffer
SCB10_EZ_DATA46	0x406A04B8	FULL	Memory buffer
SCB10_EZ_DATA47	0x406A04BC	FULL	Memory buffer
SCB10_EZ_DATA48	0x406A04C0	FULL	Memory buffer
SCB10_EZ_DATA49	0x406A04C4	FULL	Memory buffer
SCB10_EZ_DATA50	0x406A04C8	FULL	Memory buffer
SCB10_EZ_DATA51	0x406A04CC	FULL	Memory buffer
SCB10_EZ_DATA52	0x406A04D0	FULL	Memory buffer
SCB10_EZ_DATA53	0x406A04D4	FULL	Memory buffer
SCB10_EZ_DATA54	0x406A04D8	FULL	Memory buffer
SCB10_EZ_DATA55	0x406A04DC	FULL	Memory buffer
SCB10_EZ_DATA56	0x406A04E0	FULL	Memory buffer
SCB10_EZ_DATA57	0x406A04E4	FULL	Memory buffer
SCB10_EZ_DATA58	0x406A04E8	FULL	Memory buffer
SCB10_EZ_DATA59	0x406A04EC	FULL	Memory buffer
SCB10_EZ_DATA60	0x406A04F0	FULL	Memory buffer
SCB10_EZ_DATA61	0x406A04F4	FULL	Memory buffer
SCB10_EZ_DATA62	0x406A04F8	FULL	Memory buffer
SCB10_EZ_DATA63	0x406A04FC	FULL	Memory buffer
SCB10_EZ_DATA64	0x406A0500	FULL	Memory buffer
SCB10_EZ_DATA65	0x406A0504	FULL	Memory buffer
SCB10_EZ_DATA66	0x406A0508	FULL	Memory buffer
SCB10_EZ_DATA67	0x406A050C	FULL	Memory buffer
SCB10_EZ_DATA68	0x406A0510	FULL	Memory buffer
SCB10_EZ_DATA69	0x406A0514	FULL	Memory buffer
SCB10_EZ_DATA70	0x406A0518	FULL	Memory buffer
SCB10_EZ_DATA71	0x406A051C	FULL	Memory buffer
SCB10_EZ_DATA72	0x406A0520	FULL	Memory buffer
SCB10_EZ_DATA73	0x406A0524	FULL	Memory buffer
SCB10_EZ_DATA74	0x406A0528	FULL	Memory buffer
SCB10_EZ_DATA75	0x406A052C	FULL	Memory buffer
SCB10_EZ_DATA76	0x406A0530	FULL	Memory buffer
SCB10_EZ_DATA77	0x406A0534	FULL	Memory buffer
SCB10_EZ_DATA78	0x406A0538	FULL	Memory buffer
SCB10_EZ_DATA79	0x406A053C	FULL	Memory buffer
SCB10_EZ_DATA80	0x406A0540	FULL	Memory buffer
SCB10_EZ_DATA81	0x406A0544	FULL	Memory buffer
SCB10_EZ_DATA82	0x406A0548	FULL	Memory buffer
SCB10_EZ_DATA83	0x406A054C	FULL	Memory buffer
SCB10_EZ_DATA84	0x406A0550	FULL	Memory buffer
SCB10_EZ_DATA85	0x406A0554	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB10_EZ_DATA86	0x406A0558	FULL	Memory buffer
SCB10_EZ_DATA87	0x406A055C	FULL	Memory buffer
SCB10_EZ_DATA88	0x406A0560	FULL	Memory buffer
SCB10_EZ_DATA89	0x406A0564	FULL	Memory buffer
SCB10_EZ_DATA90	0x406A0568	FULL	Memory buffer
SCB10_EZ_DATA91	0x406A056C	FULL	Memory buffer
SCB10_EZ_DATA92	0x406A0570	FULL	Memory buffer
SCB10_EZ_DATA93	0x406A0574	FULL	Memory buffer
SCB10_EZ_DATA94	0x406A0578	FULL	Memory buffer
SCB10_EZ_DATA95	0x406A057C	FULL	Memory buffer
SCB10_EZ_DATA96	0x406A0580	FULL	Memory buffer
SCB10_EZ_DATA97	0x406A0584	FULL	Memory buffer
SCB10_EZ_DATA98	0x406A0588	FULL	Memory buffer
SCB10_EZ_DATA99	0x406A058C	FULL	Memory buffer
SCB10_EZ_DATA100	0x406A0590	FULL	Memory buffer
SCB10_EZ_DATA101	0x406A0594	FULL	Memory buffer
SCB10_EZ_DATA102	0x406A0598	FULL	Memory buffer
SCB10_EZ_DATA103	0x406A059C	FULL	Memory buffer
SCB10_EZ_DATA104	0x406A05A0	FULL	Memory buffer
SCB10_EZ_DATA105	0x406A05A4	FULL	Memory buffer
SCB10_EZ_DATA106	0x406A05A8	FULL	Memory buffer
SCB10_EZ_DATA107	0x406A05AC	FULL	Memory buffer
SCB10_EZ_DATA108	0x406A05B0	FULL	Memory buffer
SCB10_EZ_DATA109	0x406A05B4	FULL	Memory buffer
SCB10_EZ_DATA110	0x406A05B8	FULL	Memory buffer
SCB10_EZ_DATA111	0x406A05BC	FULL	Memory buffer
SCB10_EZ_DATA112	0x406A05C0	FULL	Memory buffer
SCB10_EZ_DATA113	0x406A05C4	FULL	Memory buffer
SCB10_EZ_DATA114	0x406A05C8	FULL	Memory buffer
SCB10_EZ_DATA115	0x406A05CC	FULL	Memory buffer
SCB10_EZ_DATA116	0x406A05D0	FULL	Memory buffer
SCB10_EZ_DATA117	0x406A05D4	FULL	Memory buffer
SCB10_EZ_DATA118	0x406A05D8	FULL	Memory buffer
SCB10_EZ_DATA119	0x406A05DC	FULL	Memory buffer
SCB10_EZ_DATA120	0x406A05E0	FULL	Memory buffer
SCB10_EZ_DATA121	0x406A05E4	FULL	Memory buffer
SCB10_EZ_DATA122	0x406A05E8	FULL	Memory buffer
SCB10_EZ_DATA123	0x406A05EC	FULL	Memory buffer
SCB10_EZ_DATA124	0x406A05F0	FULL	Memory buffer
SCB10_EZ_DATA125	0x406A05F4	FULL	Memory buffer
SCB10_EZ_DATA126	0x406A05F8	FULL	Memory buffer
SCB10_EZ_DATA127	0x406A05FC	FULL	Memory buffer
SCB10_EZ_DATA128	0x406A0600	FULL	Memory buffer
SCB10_EZ_DATA129	0x406A0604	FULL	Memory buffer
SCB10_EZ_DATA130	0x406A0608	FULL	Memory buffer
SCB10_EZ_DATA131	0x406A060C	FULL	Memory buffer
SCB10_EZ_DATA132	0x406A0610	FULL	Memory buffer
SCB10_EZ_DATA133	0x406A0614	FULL	Memory buffer
SCB10_EZ_DATA134	0x406A0618	FULL	Memory buffer
SCB10_EZ_DATA135	0x406A061C	FULL	Memory buffer
SCB10_EZ_DATA136	0x406A0620	FULL	Memory buffer
SCB10_EZ_DATA137	0x406A0624	FULL	Memory buffer
SCB10_EZ_DATA138	0x406A0628	FULL	Memory buffer
SCB10_EZ_DATA139	0x406A062C	FULL	Memory buffer
SCB10_EZ_DATA140	0x406A0630	FULL	Memory buffer
SCB10_EZ_DATA141	0x406A0634	FULL	Memory buffer
SCB10_EZ_DATA142	0x406A0638	FULL	Memory buffer
SCB10_EZ_DATA143	0x406A063C	FULL	Memory buffer
SCB10_EZ_DATA144	0x406A0640	FULL	Memory buffer
SCB10_EZ_DATA145	0x406A0644	FULL	Memory buffer
SCB10_EZ_DATA146	0x406A0648	FULL	Memory buffer
SCB10_EZ_DATA147	0x406A064C	FULL	Memory buffer
SCB10_EZ_DATA148	0x406A0650	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB10_EZ_DATA149	0x406A0654	FULL	Memory buffer
SCB10_EZ_DATA150	0x406A0658	FULL	Memory buffer
SCB10_EZ_DATA151	0x406A065C	FULL	Memory buffer
SCB10_EZ_DATA152	0x406A0660	FULL	Memory buffer
SCB10_EZ_DATA153	0x406A0664	FULL	Memory buffer
SCB10_EZ_DATA154	0x406A0668	FULL	Memory buffer
SCB10_EZ_DATA155	0x406A066C	FULL	Memory buffer
SCB10_EZ_DATA156	0x406A0670	FULL	Memory buffer
SCB10_EZ_DATA157	0x406A0674	FULL	Memory buffer
SCB10_EZ_DATA158	0x406A0678	FULL	Memory buffer
SCB10_EZ_DATA159	0x406A067C	FULL	Memory buffer
SCB10_EZ_DATA160	0x406A0680	FULL	Memory buffer
SCB10_EZ_DATA161	0x406A0684	FULL	Memory buffer
SCB10_EZ_DATA162	0x406A0688	FULL	Memory buffer
SCB10_EZ_DATA163	0x406A068C	FULL	Memory buffer
SCB10_EZ_DATA164	0x406A0690	FULL	Memory buffer
SCB10_EZ_DATA165	0x406A0694	FULL	Memory buffer
SCB10_EZ_DATA166	0x406A0698	FULL	Memory buffer
SCB10_EZ_DATA167	0x406A069C	FULL	Memory buffer
SCB10_EZ_DATA168	0x406A06A0	FULL	Memory buffer
SCB10_EZ_DATA169	0x406A06A4	FULL	Memory buffer
SCB10_EZ_DATA170	0x406A06A8	FULL	Memory buffer
SCB10_EZ_DATA171	0x406A06AC	FULL	Memory buffer
SCB10_EZ_DATA172	0x406A06B0	FULL	Memory buffer
SCB10_EZ_DATA173	0x406A06B4	FULL	Memory buffer
SCB10_EZ_DATA174	0x406A06B8	FULL	Memory buffer
SCB10_EZ_DATA175	0x406A06BC	FULL	Memory buffer
SCB10_EZ_DATA176	0x406A06C0	FULL	Memory buffer
SCB10_EZ_DATA177	0x406A06C4	FULL	Memory buffer
SCB10_EZ_DATA178	0x406A06C8	FULL	Memory buffer
SCB10_EZ_DATA179	0x406A06CC	FULL	Memory buffer
SCB10_EZ_DATA180	0x406A06D0	FULL	Memory buffer
SCB10_EZ_DATA181	0x406A06D4	FULL	Memory buffer
SCB10_EZ_DATA182	0x406A06D8	FULL	Memory buffer
SCB10_EZ_DATA183	0x406A06DC	FULL	Memory buffer
SCB10_EZ_DATA184	0x406A06E0	FULL	Memory buffer
SCB10_EZ_DATA185	0x406A06E4	FULL	Memory buffer
SCB10_EZ_DATA186	0x406A06E8	FULL	Memory buffer
SCB10_EZ_DATA187	0x406A06EC	FULL	Memory buffer
SCB10_EZ_DATA188	0x406A06F0	FULL	Memory buffer
SCB10_EZ_DATA189	0x406A06F4	FULL	Memory buffer
SCB10_EZ_DATA190	0x406A06F8	FULL	Memory buffer
SCB10_EZ_DATA191	0x406A06FC	FULL	Memory buffer
SCB10_EZ_DATA192	0x406A0700	FULL	Memory buffer
SCB10_EZ_DATA193	0x406A0704	FULL	Memory buffer
SCB10_EZ_DATA194	0x406A0708	FULL	Memory buffer
SCB10_EZ_DATA195	0x406A070C	FULL	Memory buffer
SCB10_EZ_DATA196	0x406A0710	FULL	Memory buffer
SCB10_EZ_DATA197	0x406A0714	FULL	Memory buffer
SCB10_EZ_DATA198	0x406A0718	FULL	Memory buffer
SCB10_EZ_DATA199	0x406A071C	FULL	Memory buffer
SCB10_EZ_DATA200	0x406A0720	FULL	Memory buffer
SCB10_EZ_DATA201	0x406A0724	FULL	Memory buffer
SCB10_EZ_DATA202	0x406A0728	FULL	Memory buffer
SCB10_EZ_DATA203	0x406A072C	FULL	Memory buffer
SCB10_EZ_DATA204	0x406A0730	FULL	Memory buffer
SCB10_EZ_DATA205	0x406A0734	FULL	Memory buffer
SCB10_EZ_DATA206	0x406A0738	FULL	Memory buffer
SCB10_EZ_DATA207	0x406A073C	FULL	Memory buffer
SCB10_EZ_DATA208	0x406A0740	FULL	Memory buffer
SCB10_EZ_DATA209	0x406A0744	FULL	Memory buffer
SCB10_EZ_DATA210	0x406A0748	FULL	Memory buffer
SCB10_EZ_DATA211	0x406A074C	FULL	Memory buffer

Register Name	Address	Permission	Description
SCB10_EZ_DATA212	0x406A0750	FULL	Memory buffer
SCB10_EZ_DATA213	0x406A0754	FULL	Memory buffer
SCB10_EZ_DATA214	0x406A0758	FULL	Memory buffer
SCB10_EZ_DATA215	0x406A075C	FULL	Memory buffer
SCB10_EZ_DATA216	0x406A0760	FULL	Memory buffer
SCB10_EZ_DATA217	0x406A0764	FULL	Memory buffer
SCB10_EZ_DATA218	0x406A0768	FULL	Memory buffer
SCB10_EZ_DATA219	0x406A076C	FULL	Memory buffer
SCB10_EZ_DATA220	0x406A0770	FULL	Memory buffer
SCB10_EZ_DATA221	0x406A0774	FULL	Memory buffer
SCB10_EZ_DATA222	0x406A0778	FULL	Memory buffer
SCB10_EZ_DATA223	0x406A077C	FULL	Memory buffer
SCB10_EZ_DATA224	0x406A0780	FULL	Memory buffer
SCB10_EZ_DATA225	0x406A0784	FULL	Memory buffer
SCB10_EZ_DATA226	0x406A0788	FULL	Memory buffer
SCB10_EZ_DATA227	0x406A078C	FULL	Memory buffer
SCB10_EZ_DATA228	0x406A0790	FULL	Memory buffer
SCB10_EZ_DATA229	0x406A0794	FULL	Memory buffer
SCB10_EZ_DATA230	0x406A0798	FULL	Memory buffer
SCB10_EZ_DATA231	0x406A079C	FULL	Memory buffer
SCB10_EZ_DATA232	0x406A07A0	FULL	Memory buffer
SCB10_EZ_DATA233	0x406A07A4	FULL	Memory buffer
SCB10_EZ_DATA234	0x406A07A8	FULL	Memory buffer
SCB10_EZ_DATA235	0x406A07AC	FULL	Memory buffer
SCB10_EZ_DATA236	0x406A07B0	FULL	Memory buffer
SCB10_EZ_DATA237	0x406A07B4	FULL	Memory buffer
SCB10_EZ_DATA238	0x406A07B8	FULL	Memory buffer
SCB10_EZ_DATA239	0x406A07BC	FULL	Memory buffer
SCB10_EZ_DATA240	0x406A07C0	FULL	Memory buffer
SCB10_EZ_DATA241	0x406A07C4	FULL	Memory buffer
SCB10_EZ_DATA242	0x406A07C8	FULL	Memory buffer
SCB10_EZ_DATA243	0x406A07CC	FULL	Memory buffer
SCB10_EZ_DATA244	0x406A07D0	FULL	Memory buffer
SCB10_EZ_DATA245	0x406A07D4	FULL	Memory buffer
SCB10_EZ_DATA246	0x406A07D8	FULL	Memory buffer
SCB10_EZ_DATA247	0x406A07DC	FULL	Memory buffer
SCB10_EZ_DATA248	0x406A07E0	FULL	Memory buffer
SCB10_EZ_DATA249	0x406A07E4	FULL	Memory buffer
SCB10_EZ_DATA250	0x406A07E8	FULL	Memory buffer
SCB10_EZ_DATA251	0x406A07EC	FULL	Memory buffer
SCB10_EZ_DATA252	0x406A07F0	FULL	Memory buffer
SCB10_EZ_DATA253	0x406A07F4	FULL	Memory buffer
SCB10_EZ_DATA254	0x406A07F8	FULL	Memory buffer
SCB10_EZ_DATA255	0x406A07FC	FULL	Memory buffer
SCB10_INTR_CAUSE	0x406A0E00	FULL	Active clocked interrupt signal Note: I2C_EC is not available for this register
SCB10_INTR_SPI_EC	0x406A0EC0	FULL	Externally clocked SPI interrupt request
SCB10_INTR_SPI_EC_MASK	0x406A0EC8	FULL	Externally clocked SPI interrupt mask
SCB10_INTR_SPI_EC_MASKED	0x406A0ECC	FULL	Externally clocked SPI interrupt masked
SCB10_INTR_M	0x406A0F00	FULL	Master interrupt request
SCB10_INTR_M_SET	0x406A0F04	FULL	Master interrupt set request
SCB10_INTR_M_MASK	0x406A0F08	FULL	Master interrupt mask
SCB10_INTR_M_MASKED	0x406A0F0C	FULL	Master interrupt masked request
SCB10_INTR_S	0x406A0F40	FULL	Slave interrupt request
SCB10_INTR_S_SET	0x406A0F44	FULL	Slave interrupt set request
SCB10_INTR_S_MASK	0x406A0F48	FULL	Slave interrupt mask
SCB10_INTR_S_MASKED	0x406A0F4C	FULL	Slave interrupt masked request
SCB10_INTR_TX	0x406A0F80	FULL	Transmitter interrupt request
SCB10_INTR_TX_SET	0x406A0F84	FULL	Transmitter interrupt set request
SCB10_INTR_TX_MASK	0x406A0F88	FULL	Transmitter interrupt mask
SCB10_INTR_TX_MASKED	0x406A0F8C	FULL	Transmitter interrupt masked request
SCB10_INTR_RX	0x406A0FC0	FULL	Receiver interrupt request
SCB10_INTR_RX_SET	0x406A0FC4	FULL	Receiver interrupt set request

Register Name	Address	Permission	Description
SCB10_INTR_RX_MASK	0x406A0FC8	FULL	Receiver interrupt mask
SCB10_INTR_RX_MASKED	0x406A0FCC	FULL	Receiver interrupt masked request

24.12 Register Details

24.12.1 SCB_CTRL

Description: Generic control
Address: 0x40600000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x300400F

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				OVS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	MEM_WIDTH [15:14]		None [13:13]	CMD_RESP_MODE [12:12]	None [11:11]	EZ_MODE [10:10]	EC_OP_MODE [9:9]	EC_AM_MODE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						BLOCK [17:17]	ADDR_ACCEPT [16:16]

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:29]		EC_ACCESS [28:28]	None [27:26]		MODE [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	OVS	RW	RW	15	Serial interface bit period oversampling factor expressed in IP clock cycles. Used for SPI and UART functionality. OVS + 1 IP clock cycles constitute a single serial interface clock/bit cycle. The IP clock is provided by the programmable clock IP. This field is NOT used in externally clocked mode. If OVS is odd, the oversampling factor is even and the first and second phase of the interface clock period are the same. If OVS is even, the oversampling factor is odd and the first phase of the interface clock period is 1 peripheral clock cycle longer than the second phase of the interface clock period. In SPI master mode, the valid range is [3, 15]. The effective system bit rate is dependent on the external SPI slave that we communicate with. If the SPI output clock 'spi_clk_out' to SPI MISO input 'spi_miso_in' round trip delay is introducing significant delays (multiple 'spi_clk_out' cycles), it may be necessary to increase OVS and/or to set SPI_CTRL.LATE_MISO_SAMPLE to '1' to achieve the maximum possible system bit rate. The required IP clock/IF clock ratio increases and the calculated maximum bit rate decreases, when realistic chip and routing delays are taken into account. for SPI master with MOSI only (transmission only), the valid range is [1, 15]. In SPI slave mode, the OVS field is NOT used. However, there is a frequency requirement for the IP clock wrt. the interface (IF) clock to guarantee functional correct behavior. This requirement is expressed as a ratio: IP clock/IF clock. The ratio is dependent on the setting of RX_CTRL.MEDIAN and the external SPI master's capability to support 'late MISO sample' functionality (similar to our SPI master functionality represented by SPI_CTRL.LATE_MISO_SAMPLE): - MEDIAN is '0' and external SPI master has NO 'late MISO sample functionality': IP clock/IF clock $\geq$ 6. - MEDIAN is '0' and external SPI master has 'late MISO sample functionality': IP clock/IF clock $\geq$ 3. - MEDIAN is '1' and external SPI master has NO 'late MISO sample functionality': IP clock/IF clock $\geq$ 8. - MEDIAN is '1' and external SPI master has 'late MISO sample functionality': IP clock/IF clock $\geq$ 4. The maximum bit rates provide an IP centric perspective, assuming ideal (0 ns) IO cell and routing (chip and board) delay. The required IP clock/IF clock ratio increases and the calculated maximum bit rate decreases, when realistic chip and routing delays are taken into account. In UART standard submodule (including LIN), the valid range is [7, 15]. In UART SmartCard submodule, the valid range is [7, 15].

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) In UART TX IrDA submode this field indirectly specifies the oversampling. The oversampling determines the interface clock/bit cycle and the width of the pulse. Only normal transmission mode is supported, the pulse is roughly 3/16 of the bit period (for all bit rates). There is only one valid OVS value: - 0: 16 times oversampling. IP clock frequency of 16*115.2 KHz for 115.2 Kbps. IP clock frequency of 16*57.6 KHz for 57.6 Kbps. IP clock frequency of 16*38.4 KHz for 38.4 Kbps. IP clock frequency of 16*19.2 KHz for 19.2 Kbps. IP clock frequency of 16*9.6 KHz for 9.6 Kbps. IP clock frequency of 16*2.4 KHz for 2.4 Kbps. IP clock frequency of 16*1.2 KHz for 1.2 Kbps. - all other values are not used in normal mode. In UART RX IrDA submode (1.2, 2.4, 9.6, 19.2, 38.4, 57.6 and 115.2 Kbps) this field indirectly specifies the oversampling. The oversampling determines the interface clock/bit cycle and the width of the pulse. In normal transmission mode, this pulse is roughly 3/16 of the bit period (for all bit rates). In low power transmission mode, this pulse is potentially smaller (down to 1.62 us typical and 1.41 us minimal) than 3/16 of the bit period (for < 115.2 Kbps bitrates). Pulse widths greater or equal than two IP clock cycles are guaranteed to be detected by the receiver. Pulse widths less than two IP clock cycles and greater or equal than one IP clock cycle may be detected by the receiver. Pulse widths less than one IP clock cycle will not be detected by the receiver. RX_CTRL.MEDIAN should be set to '1' for IrDA receiver functionality. The IP clock (as provided by the programmable clock IP) and the oversampling together determine the IrDA bitrate. Normal mode, OVS field values (with the required IP clock frequency): - 0: 16 times oversampling. IP clock frequency of 16*115.2 KHz for 115.2 Kbps. IP clock frequency of 16*57.6 KHz for 57.6 Kbps. IP clock frequency of 16*38.4 KHz for 38.4 Kbps. IP clock frequency of 16*19.2 KHz for 19.2 Kbps. IP clock frequency of 16*9.6 KHz for 9.6 Kbps. IP clock frequency of 16*2.4 KHz for 2.4 Kbps. IP clock frequency of 16*1.2 KHz for 1.2 Kbps. - all other values are not used in normal mode. Low power mode, OVS field values (with the required IP clock frequency): - 0: 16 times oversampling. - 1: 32 times oversampling. - 2: 48 times oversampling. - 3: 96 times oversampling. - 4: 192 times oversampling.

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) IP clock frequency of 192*9.6 KHz for 9.6 Kbps. - 5: 768 times oversampling. IP clock frequency of 768*2.4 KHz for 2.4 Kbps. - 6: 1536 times oversampling. IP clock frequency of 1536*1.2 KHz for 1.2 Kbps. - all other values are not used in low power mode.
8	EC_AM_MODE	RW	RW	0	Internally clocked mode ('0') or externally clocked mode ('1') address matching (I2C) or selection (SPI). In internally clocked mode, the serial interface protocols run off the peripheral clock. In externally clocked mode, the serial interface protocols run off the clock as provided by the serial interface. Externally clocked mode is only used for synchronous serial interface protocols (SPI and I2C) in slave mode. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported. In UART mode this field should be '0'.
9	EC_OP_MODE	RW	RW	0	Internally clocked mode ('0') or externally clocked mode ('1') operation. In internally clocked mode, the serial interface protocols run off the peripheral clock. In externally clocked mode, the serial interface protocols run off the clock as provided by the serial interface. Externally clocked operation mode is only used for synchronous serial interface protocols (SPI and I2C) in slave mode AND EZ mode. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported. The maximum SPI slave, EZ mode bitrate is 48 Mbps (transmission and IO delays outside the IP will degrade the effective bitrate). In UART mode this field should be '0'.
10	EZ_MODE	RW	RW	0	Non EZ mode ('0') or EZ mode ('1'). In EZ mode, a meta protocol is applied to the serial interface protocol. This meta protocol adds meaning to the data frames transferred by the serial interface protocol: a data frame can represent a memory address, a write memory data element or a read memory data element. EZ mode is only used for synchronous serial interface protocols: SPI and I2C. In SPI mode, only Motorola submode (all Motorola modes: 0, 1, 2, 3) is supported and the transmitter should use continuous data frames; i.e. data frames not separated by slave deselection. This mode is only applicable to slave functionality. In EZ mode, the slave can read from and write to an addressable memory structure of up to 256 bytes. In EZ mode, data frames should 8-bit in size and should be transmitted and received with the Most Significant Bit (MSB) first. In UART mode this field should be '0'.
12	CMD_RESP_MODE	RW	RW	0	Determines CMD_RESP mode of operation: '0': CMD_RESP mode disabled. '1': CMD_RESP mode enabled (also requires EC_AM_MODE and EC_OP_MODE to be set to '1').
14:15	MEM_WIDTH	RW	RW	1	Determines the number of bits per FIFO data element.
	BYTE			0	8-bit FIFO data elements. This mode provides the biggest amount of FIFO entries, but TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH are restricted to [0, 7].

Bits	Name	SW	HW	Default or Enum	Description
	HALFWORD			1	16-bit FIFO data elements. TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH are restricted to [0, 15].
	WORD			2	32-bit FIFO data elements. This mode provides the smallest amount of FIFO entries, but TX_CTRL.DATA_WIDTH and RX_CTRL.DATA_WIDTH can be in a range of [0, 31].
	Reserved			3	N/A
16	ADDR_ACCEPT	RW	RW	0	Determines whether a received matching address is accepted in the RX FIFO ('1') or not ('0'). In I2C mode, this field is used to allow the slave to put the received slave address or general call address in the RX FIFO. Note that a received matching address is put in the RX FIFO when ADDR_ACCEPT is '1' for both I2C read and write transfers. In multi-processor UART receiver mode, this field is used to allow the receiver to put the received address in the RX FIFO. Note: non-matching addresses are never put in the RX FIFO.
17	BLOCK	RW	RW	0	Only used in externally clocked mode. If the externally clocked logic and the MMIO SW accesses to EZ memory coincide/collide, this bit determines whether a SW access should block and result in bus wait states ('BLOCK is 1') or not ('BLOCK is 0'). IF BLOCK is '0' and the accesses collide, MMIO read operations return 0xffff:ffff and MMIO write operations are ignored. Colliding accesses are registered as interrupt causes: field BLOCKED of MMIO registers INTR_TX and INTR_RX.
24:25	MODE	RW	RW	3	Mode of operation (3: Reserved)
	I2C			0	Inter-Integrated Circuits (I2C) mode.
	SPI			1	Serial Peripheral Interface (SPI) mode.
	UART			2	Universal Asynchronous Receiver/Transmitter (UART) mode.
28	EC_ACCESS	RW	RW	0	used to enable I2CS_EC or SPIS_EC access to internal SRAM memory. 0: enable clock_scb_en, has no effect on ec_busy_pp 1: disable clock_scb_en, enable ec_busy_pp (grant I2CS_EC or SPIS_EC access) Before going to deepsleep this field should be set to 1. when waking up from DeepSleep power mode, and PLL is locked (clk_scb is at expected frequency), this filed should be set to 0.

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLED	RW	RW	0	IP enabled ('1') or not ('0'). The proper order in which to initialize the IP is as follows: - Program protocol specific information using SPI_CTRL, UART_CTRL (and UART_TX_CTRL and UART_RX_CTRL) or I2C_CTRL. This includes selection of a submode, master/slave functionality and transmitter/receiver functionality when applicable. - Program generic transmitter (TX_CTRL) and receiver (RX_CTRL) information. This includes enabling of the transmitter and receiver functionality. - Program transmitter FIFO (TX_FIFO_CTRL) and receiver FIFO (RX_FIFO_CTRL) information. - Program CTRL to enable IP, select the specific operation mode and oversampling factor. Generally when the IP is enabled, no control information should be changed. Changes should be made AFTER disabling the IP, e.g. to modify the operation mode (from I2C to SPI) or to go from externally to internally clocked. The change takes effect after the IP is re-enabled. Note that disabling the IP will cause re-initialization of the design and associated state is lost (e.g. FIFO content). Specific to SPI master case, when SCB is idle, below registers can be changed without disabling SCB block, TX_CTRL TX_FIFO_CTRL RX_CTRL RX_FIFO_CTRL SPI_CTRL.SSEL,

24.12.2 SCB_STATUS

Description: Generic status
Address: 0x40600004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							EC_BUSY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	EC_BUSY	R	R	Undefined	Indicates whether the externally clocked logic is potentially accessing the EZ memory (this is only possible in EZ mode). This bit can be used by SW to determine whether it is safe to issue a SW access to the EZ memory (without bus wait states (a blocked SW access) or bus errors being generated). Note that the INTR_TX.BLOCKED and INTR_RX.BLOCKED interrupt causes are used to indicate whether a SW access was actually blocked by externally clocked logic.

24.12.3 SCB_CMD_RESP_CTRL

Description: Command/response control
Address: 0x40600008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BASE_RD_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							BASE_RD_ADDR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	BASE_WR_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							BASE_WR_ADDR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	BASE_RD_ADDR	RW	RW	0	I2C/SPI read base address for CMD_RESP mode. Address is used by a I2C CMD_RESP mode read transfer (CTRL.MODE is I2C) or a SPI CMD_RESP mode read transfer (CTRL.MODE is SPI): at the start of a read transfer BASE_RD_ADDR is copied to CMD_RESP_STATUS.CURR_RD_ADDR. This field should not be modified during ongoing bus transfers.
16:24	BASE_WR_ADDR	RW	RW	0	I2C/SPI write base address for CMD_RESP mode. Address is used by a I2C CMD_RESP mode write transfer (CTRL.MODE is I2C) or a SPI CMD_RESP mode write transfer (CTRL.MODE is SPI): at the start of a write transfer BASE_WE_ADDR is copied to CMD_RESP_STATUS.CURR_WR_ADDR. This field should not be modified during ongoing bus transfers.

24.12.4 SCB_CMD_RESP_STATUS

Description: Command/response status

Address: 0x4060000C

Offset: 0xC

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields reflect register states without a default/reset value (CURR_RD_ADDR and CURR_WR_ADDR) or reflect an external bus state. Therefore, these registers are undefined after the IP is enabled.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CURR_RD_ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							CURR_RD_ADDR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	CURR_WR_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CMD_RESP_EC_BUSY [31:31]	CMD_RESP_EC_BUS_BUSY [30:30]	None [29:25]					CURR_WR_ADDR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	CURR_RD_ADDR	R	R	Undefined	I2C/SPI read current address for CMD_RESP mode. HW increments the field after a read access to the memory buffer. However, when the last memory buffer address is reached, the address is NOT incremented (but remains at the maximum memory buffer address). The field is used to determine how many bytes have been read (# bytes = CURR_RD_ADDR - CMD_RESP_CTRL.BASE_RD_ADDR). This field is reliable during when there is no bus transfer. This field is potentially unreliable when there is a bus transfer bus transfer: when CMD_RESP_EC_BUSY is '0', the field is reliable.
16:24	CURR_WR_ADDR	R	R	Undefined	I2C/SPI write current address for CMD_RESP mode. HW increments the field after a read access to the memory buffer. However, when the last memory buffer address is reached, the address is NOT incremented (but remains at the maximum memory buffer address). The field is used to determine how many bytes have been written (# bytes = CURR_WR_ADDR - CMD_RESP_CTRL.BASE_WR_ADDR). This field is reliable during when there is no bus transfer. This field is potentially unreliable when there is a bus transfer bus transfer: when CMD_RESP_EC_BUSY is '0', the field is reliable.

Bits	Name	SW	HW	Default or Enum	Description
30	CMD_RESP_EC_BUSY	R	R	Undefined	Indicates whether there is an ongoing bus transfer to the IP. '0': no ongoing bus transfer. '1': ongoing bus transfer. For SPI, the field is '1' when the slave is selected. For I2C, the field is set to '1' at a I2C START/RESTART. In case of an address match, the field is set to '0' on a I2C STOP. In case of NO address match, the field is set to '0' after the failing address match.
31	CMD_RESP_EC_BUSY	R	R	Undefined	Indicates whether the CURR_RD_ADDR and CURR_WR_ADDR fields in this register are reliable (when CMD_RESP_EC_BUSY is '0') or not reliable (when CMD_RESP_EC_BUSY is '1'). Note: - When there is no ongoing bus transfer, CMD_RESP_EC_BUSY is '0' (reliable). - When there is a ongoing bus transfer, CMD_RESP_EC_BUSY is '0' (reliable), when the CURR_RD_ADDR and CURR_WR_ADDR are not being updated by the HW. - When there is a ongoing bus transfer, CMD_RESP_EC_BUSY is '1' (not reliable), when the CURR_RD_ADDR or CURR_WR_ADDR are being updated by the HW. Note that this update lasts one I2C clock cycle, or two SPI clock cycles.

24.12.5 SCB_SPI_CTRL

Description: SPI control
Address: 0x40600020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3000010

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		SCLK CONT INUOUS [5:5]	LATE MISO _SAMPLE [4:4]	CPOL [3:3]	CPHA [2:2]	SELECT _PRECEDE [1:1]	SSEL CONT INUOUS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	SSEL_INTE R_FRAME _DEL [14:14]	SSEL _HOLD _DEL [13:13]	SSEL _SETUP _DEL [12:12]	SSEL _POLA _RITY3 [11:11]	SSEL _POLA _RITY2 [10:10]	SSEL _POLA _RITY1 [9:9]	SSEL _POLA _RITY0 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							LOOPBACK [16:16]

Bits	31	30	29	28	27	26	25	24
Name	MASTER _MODE [31:31]	None [30:28]			SSEL [27:26]		MODE [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SSEL_CONTINUOUS	RW	RW	0	Continuous SPI data transfers enabled ('1') or not ('0'). This field is used in master mode. In slave mode, both continuous and non-continuous SPI data transfers are supported independent of this field. When continuous transfers are enabled individual data frame transfers are not necessarily separated by slave deselection (as indicated by the level or pulse on the SELECT line): if the TX FIFO has multiple data frames, data frames are send out without slave deselection. When continuous transfers are not enabled individual data frame transfers are always separated by slave deselection: data frames are always separated by slave deselection.
1	SELECT_PRECEDE	RW	RW	0	Only used in SPI Texas Instruments' submode. When '1', the data frame start indication is a pulse on the SELECT line that precedes the transfer of the first data frame bit. When '0', the data frame start indication is a pulse on the SELECT line that coincides with the transfer of the first data frame bit.

Bits	Name	SW	HW	Default or Enum	Description
2	CPHA	RW	RW	0	Indicates the clock phase. This field, together with the CPOL field, indicates when MOSI data is driven and MISO data is captured: - Motorola mode 0. CPOL is '0', CPHA is '0': MOSI is driven on a falling edge of SCLK. MISO is captured on a rising edge of SCLK. - Motorola mode 1. CPOL is '0', CPHA is '1': MOSI is driven on a rising edge of SCLK. MISO is captured on a falling edge of SCLK. - Motorola mode 2. CPOL is '1', CPHA is '0': MOSI is driven on a rising edge of SCLK. MISO is captured on a falling edge of SCLK. - Motorola mode 3. CPOL is '1', CPHA is '1': MOSI is driven on a falling edge of SCLK. MISO is captured on a rising edge of SCLK. In SPI Motorola submode, all four CPOL/CPHA modes are valid. in SPI NS submode, only CPOL=0 CPHA=0 mode is valid. in SPI TI submode, only CPOL=0 CPHA=1 mode is valid.
3	CPOL	RW	RW	0	Indicates the clock polarity. This field, together with the CPHA field, indicates when MOSI data is driven and MISO data is captured: - CPOL is '0': SCLK is '0' when not transmitting data. - CPOL is '1': SCLK is '1' when not transmitting data.
4	LATE_MISO_SAMPLE	RW	RW	1	Changes the SCLK edge on which MISO is captured. Only used in master mode. When '0', the default applies (for Motorola as determined by CPOL and CPHA, for Texas Instruments on the falling edge of SCLK and for National Semiconductors on the rising edge of SCLK). When '1', the alternate clock edge is used (which comes half a SPI SCLK period later). Late sampling addresses the round trip delay associated with transmitting SCLK from the master to the slave and transmitting MISO from the slave to the master.
5	SCLK_CONTINUOUS	RW	RW	0	Only applicable in master mode. '0': SCLK is generated, when the SPI master is enabled and data is transmitted. '1': SCLK is generated, when the SPI master is enabled. This mode is useful for slave devices that use SCLK for functional operation other than just SPI functionality.
8	SSEL_POLARITY0	RW	RW	0	Slave select polarity. SSEL_POLARITY0 applies to the outgoing SPI slave select signal 0 (master mode) and to the incoming SPI slave select signal (slave mode). For Motorola and National Semiconductors submodes: '0': slave select is low/'0' active. '1': slave select is high/'1' active. For Texas Instruments submode: '0': high/'1' active precede/coincide pulse. '1': low/'0' active precede/coincide pulse.
9	SSEL_POLARITY1	RW	RW	0	Slave select polarity.
10	SSEL_POLARITY2	RW	RW	0	Slave select polarity.
11	SSEL_POLARITY3	RW	RW	0	Slave select polarity.

Bits	Name	SW	HW	Default or Enum	Description
12	SSEL_SETUP_DEL	RW	RW	0	Indicates the SPI SELECT setup delay (between SELECT activation and SCLK clock edge to sample the first MOSI bit). '0': 0.75 SPI clock cycles '1': 1.75 SPI clock cycles Only applies in SPI MOTOROLA submode and when SCLK_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle.
13	SSEL_HOLD_DEL	RW	RW	0	Indicates the SPI SELECT hold delay (between SPI clock edge to sample the last MOSI bit, and SELECT deactivation). '0': 0.75 SPI clock cycles '1': 1.75 SPI clock cycles Only applies in SPI MOTOROLA submode and when SCLK_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle.
14	SSEL_INTER_FRAME_DEL	RW	RW	0	Indicates the SPI SELECT inter-dataframe delay (between SELECT deactivation and SELECT activation). '0': 1.5 SPI clock cycles '1': 2.5 SPI clock cycles Only applies in SPI MOTOROLA submode and when SPI_CTRL.SSEL_CONTINUOUS=0, CTRL.OVS>=3. above are ideal case at SCB block level, and there is inaccuracy of one clk_scb cycle.
16	LOOPBACK	RW	RW	0	Local loopback control (does NOT affect the information on the pins). Only used in master mode. Not used in National Semiconductors submode. '0': the SPI master MISO line 'spi_miso_in' is connected to the SPI MISO pin. '1': the SPI master MISO line 'spi_miso_in' is connected to the SPI master MOSI line 'spi_mosi_out'. In other words, in loopback mode the SPI master receives on MISO what it transmits on MOSI.
24:25	MODE	RW	RW	3	Submode of SPI operation (3: Reserved).
	SPI_MOTOROLA			0	SPI Motorola submode. In master mode, when not transmitting data (SELECT is inactive), SCLK is stable at CPOL. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), SELECT is inactive.
	SPI_TI			1	SPI Texas Instruments submode. In master mode, when not transmitting data, SCLK is stable at '0'. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), SELECT is inactive; i.e. no pulse is generated.
	SPI_NS			2	SPI National Semiconductors submode. In master mode, when not transmitting data, SCLK is stable at '0'. In slave mode, when not selected, SCLK is ignored; i.e. it can be either stable or clocking. In master mode, when there is no data to transmit (TX FIFO is empty), SELECT is inactive.

Bits	Name	SW	HW	Default or Enum	Description
26:27	SSEL	RW	RW	0	Selects one of the four incoming/outgoing SPI slave select signals: - 0: Slave 0, SSEL[0]. - 1: Slave 1, SSEL[1]. - 2: Slave 2, SSEL[2]. - 3: Slave 3, SSEL[3]. The IP should be disabled when changes are made to this field.
31	MASTER_MODE	RW	RW	0	Master ('1') or slave ('0') mode. In master mode, transmission will commence on availability of data frames in the TX FIFO. In slave mode, when selected and there is no data frame in the TX FIFO, the slave will transmit all '1's. In both master and slave modes, received data frames will be lost if the RX FIFO is full.

24.12.6 SCB_SPI_STATUS

Description: SPI status
Address: 0x40600024
Offset: 0x24
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						SPI_EC_BUSY [1:1]	BUS_BUSY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	CURR_EZ_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BASE_EZ_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BUS_BUSY	R	R	Undefined	SPI bus is busy. The bus is considered busy ('1') during an ongoing transaction. For Motorola and National submodes, the busy bit is '1', when the slave selection is activated. For TI submode, the busy bit is '1' from the time the preceding/coinciding slave select is activated for the first transmitted data frame, till the last MOSI/MISO bit of the last data frame is transmitted.
1	SPI_EC_BUSY	R	R	Undefined	Indicates whether the externally clocked logic is potentially accessing the EZ memory and/or updating BASE_ADDR or CURR_ADDR (this is only possible in EZ mode). This bit can be used by SW to determine whether BASE_ADDR and CURR_ADDR are reliable.
8:15	CURR_EZ_ADDR	R	R	Undefined	SPI current EZ address. Current address pointer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable (during an ongoing transfer when SPI_EC_BUSY is '1'), as clock domain synchronization is not performed in the design.
16:23	BASE_EZ_ADDR	R	R	Undefined	SPI base EZ address. Address as provided by a SPI write transfer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable, as clock domain synchronization is not performed in the design.

24.12.7 SCB_SPI_TX_CTRL

Description: SPI transmitter control
Address: 0x40600028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment: Only applies in SPI MOTOROLA submode, internally clocked SPI operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		PARITY_ENABLED [5:5]	PARITY [4:4]	None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4	PARITY	RW	RW	0	Parity bit. When '0', the transmitter generates an even parity. When '1', the transmitter generates an odd parity.
5	PARITY_ENABLED	RW	RW	0	Parity generation enabled ('1') or not ('0').

24.12.8 SCB_SPI_RX_CTRL

Description: SPI receiver control
Address: 0x4060002C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment: Only applies in SPI MOTOROLA submode, internally clocked SPI operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		PARITY_ENABLED [5:5]	PARITY [4:4]	None [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							DROP_ON_PARITY_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
4	PARITY	RW	RW	0	Parity bit. When '0', the receiver expects an even parity. When '1', the receiver expects an odd parity.
5	PARITY_ENABLED	RW	RW	0	Parity checking enabled ('1') or not ('0').
8	DROP_ON_PARITY_ERROR	RW	RW	0	Behavior when a parity check fails. When '0', received data is send to the RX FIFO. When '1', received data is dropped and lost.

24.12.9 SCB_UART_CTRL

Description: UART control
Address: 0x40600040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x3000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							LOOPBACK [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						MODE [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16	LOOPBACK	RW	RW	0	Local loopback control (does NOT affect the information on the pins). When '0', the transmitter TX line 'uart_tx_out' is connected to the TX pin and the receiver RX line 'uart_rx_in' is connected to the RX pin. When '1', the transmitter TX line 'uart_tx_out' is connected to the receiver RX line 'uart_rx_in'. A similar connections scheme is followed for 'uart_rts_out' and 'uart_cts_in'. This allows a SCB UART transmitter to communicate with its receiver counterpart.
24:25	MODE	RW	RW	3	Submode of UART operation (3: Reserved)
	UART_STD			0	Standard UART submode.
	UART_SMARTCARD			1	SmartCard (ISO7816) submode. Support for negative acknowledgement (NACK) on the receiver side and retransmission on the transmitter side.
	UART_IRDA			2	Infrared Data Association (IrDA) submode. Return to Zero modulation scheme.

24.12.10 SCB_UART_TX_CTRL

Description: UART transmitter control
Address: 0x40600044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		PARITY_ENABLED [5:5]	PARITY [4:4]	None [3:3]	STOP_BITS [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							RETRY_ON_NACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	STOP_BITS	RW	RW	2	Stop bits. STOP_BITS + 1 is the duration of the stop period in terms of halve bit periods. Valid range is [1, 7]; i.e. a stop period should last at least one bit period.
4	PARITY	RW	RW	0	Parity bit. When '0', the transmitter generates an even parity. When '1', the transmitter generates an odd parity. Only applicable in standard UART and SmartCard submodes.
5	PARITY_ENABLED	RW	RW	0	Parity generation enabled ('1') or not ('0'). Only applicable in standard UART submodes. In SmartCard submode, parity generation is always enabled through hardware. In IrDA submode, parity generation is always disabled through hardware
8	RETRY_ON_NACK	RW	RW	0	When '1', a data frame is retransmitted when a negative acknowledgement is received. Only applicable to the SmartCard submode.

24.12.11 SCB_UART_RX_CTRL

Description: UART receiver control
Address: 0x40600048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xA0002

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	POLARITY [6:6]	PARITY_ENABLED [5:5]	PARITY [4:4]	None [3:3]	STOP_BITS [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		SKIP_START [13:13]	LIN_MODE [12:12]	None [11:11]	MP_MODE [10:10]	DROP_ON_FRAME_ERROR [9:9]	DROP_ON_PARITY_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				BREAK_WIDTH [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:25]							BREAK_LEVEL [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	STOP_BITS	RW	RW	2	Stop bits. STOP_BITS + 1 is the duration of the stop period in terms of halve bit periods. Valid range is [1, 7]; i.e. a stop period should last at least one bit period. Note that in case of a stop bits error, the successive data frames may get lost as the receiver needs to resynchronize its start bit detection. The amount of lost data frames depends on both the amount of stop bits, the idle ('1') time between data frames and the data frame value.
4	PARITY	RW	RW	0	Parity bit. When '0', the receiver expects an even parity. When '1', the receiver expects an odd parity. Only applicable in standard UART and SmartCard submodes.
5	PARITY_ENABLED	RW	RW	0	Parity checking enabled ('1') or not ('0'). Only applicable in standard UART submode. In SmartCard submode, parity checking is always enabled through hardware. In IrDA submode, parity checking is always disabled through hardware.
6	POLARITY	RW	RW	0	Inverts incoming RX line signal 'uart_rx_in'. Inversion is after local loopback. This functionality is intended for IrDA receiver functionality.
8	DROP_ON_PARITY_ERROR	RW	RW	0	Behavior when a parity check fails. When '0', received data is send to the RX FIFO. When '1', received data is dropped and lost. Only applicable in standard UART and SmartCard submodes (negatively acknowledged SmartCard data frames may be dropped with this field).

Bits	Name	SW	HW	Default or Enum	Description
9	DROP_ON_FRAME_ERROR	RW	RW	0	Behavior when an error is detected in a start or stop period. When '0', received data is send to the RX FIFO. When '1', received data is dropped and lost.
10	MP_MODE	RW	RW	0	Multi-processor mode. When '1', multi-processor mode is enabled. In this mode, RX_CTRL.DATA_WIDTH should indicate a 9-bit data frame. In multi-processor mode, the 9th received bit of a data frame separates addresses (bit is '1') from data (bit is '0'). A received address is matched with RX_MATCH.DATA and RX_MATCH.MASK. In the case of a match, subsequent received data are sent to the RX FIFO. In the case of NO match, subsequent received data are dropped.
12	LIN_MODE	RW	RW	0	Only applicable in standard UART submode. When '1', the receiver performs break detection and baud rate detection on the incoming data. First, break detection counts the amount of bit periods that have a line value of '0'. BREAK_WIDTH specifies the minimum required amount of bit periods. Successful break detection sets the INTR_RX.BREAK_DETECT interrupt cause to '1'. Second, baud rate detection counts the amount of peripheral clock periods that are use to receive the synchronization byte (0x55; least significant bit first). The count is available through UART_RX_STATUS.BR_COUNTER. Successful baud rate detection sets the INTR_RX.BAUD_DETECT interrupt cause to '1' (BR_COUNTER is reliable). This functionality is used to synchronize/refine the receiver clock to the transmitter clock. The receiver software can use the BR_COUNTER value to set the right IP clock (from the programmable clock IP) to guarantee successful receipt of the first LIN data frame (Protected Identifier Field) after the synchronization byte.
13	SKIP_START	RW	RW	0	Only applicable in standard UART submode. When '1', the receiver skips start bit detection for the first received data frame. Instead, it synchronizes on the first received data frame bit, which should be a '1'. This functionality is intended for wake up from DeepSleep when receiving a data frame. The transition from idle ('1') to START ('0') on the RX line is used to wake up the CPU. The transition detection (and the associated wake up functionality) is performed by the GPIO2 IP. The woken up CPU will enable the SCB's UART receiver functionality. Once enabled, it is assumed that the START bit is ongoing (the CPU wakeup and SCB enable time should be less than the START bit period). The SCB will synchronize to a '0' to '1' transition, which indicates the first data frame bit is received (first data frame bit should be '1'). After synchronization to the first data frame bit, the SCB will resume normal UART functionality: subsequent data frames will be synchronized on the receipt of a START bit.

Bits	Name	SW	HW	Default or Enum	Description
16:19	BREAK_WIDTH	RW	RW	10	Break width. BREAK_WIDTH + 1 is the minimum width in bit periods of a break. During a break the transmitted/received line value is '0'. This feature is useful for standard UART submode and LIN submode ('break field' detection). Once, the break is detected, the INTR_RX.BREAK_DETECT bit is set to '1'. Note that break detection precedes baud rate detection, which is used to synchronize/refine the receiver clock to the transmitter clock. As a result, break detection operates with an unsynchronized/unrefined receiver clock. Therefore, the receiver's definition of a bit period is imprecise and the setting of this field should take this imprecision into account. The LIN standard also accounts for this imprecision: a LIN start bit followed by 8 data bits allows for up to 9 consecutive '0' bit periods during regular transmission, whereas the LIN break detection should be at least 13 consecutive '0' bit periods. This provides for a margin of 4 bit periods. Therefore, the default value of this field is set to 10, representing a minimal break field with of $10+1 = 11$ bit periods; a value in between the 9 consecutive bit periods of a regular transmission and the 13 consecutive bit periods of a break field. This provides for slight imprecisions of the receiver clock wrt. the transmitter clock. There should not be a need to program this field to any value other than its default value.
24	BREAK_LEVEL	RW	RW	0	0: low level pulse detection, like Break field in LIN protocol 1: high level pulse detection, like IFS field in CXPI protocol, or idle line state in UART

24.12.12 SCB_UART_RX_STATUS

Description: UART receiver status
Address: 0x4060004C
Offset: 0x4C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BR_COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BR_COUNTER [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:11	BR_COUNTER	R	R	Undefined	Amount of peripheral clock periods that constitute the transmission of a 0x55 data frame (sent least significant bit first) as determined by the receiver. BR_COUNTER / 8 is the amount of peripheral clock periods that constitute a bit period. This field has valid data when INTR_RX.BAUD_DETECT is set to '1'.

24.12.13 SCB_UART_FLOW_CTRL

Description: UART flow control

Address: 0x40600050

Offset: 0x50

Retention: Retained

IsDeepSleep: No

Comment: UART flow control is a design time configuration parameter, which make the presence of this MMIO register conditional to the configuration. The 'uart_rts_out' and 'uart_cts_in' are always present on the IP interface. If flow control is configured out, 'uart_rts_out' is NOT connected, and 'uart_cts_in' should be connected to '0'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGGER_LEVEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							RTS_POLARITY [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						CTS_ENABLED [25:25]	CTS_POLARITY [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGGER_LEVEL	RW	RW	0	Trigger level. When the receiver FIFO has less entries than the amount of this field, a Ready To Send (RTS) output signal 'uart_rts_out' is activated. By setting this field to '0', flow control is effectively SW disabled (may be useful for debug purposes).
16	RTS_POLARITY	RW	RW	0	Polarity of the RTS output signal 'uart_rts_out': '0': RTS is low/'0' active; 'uart_rts_out' is '0' when active and 'uart_rts_out' is '1' when inactive. '1': RTS is high/'1' active; 'uart_rts_out' is '1' when active and 'uart_rts_out' is '0' when inactive. During IP reset (Hibernate system power mode), 'uart_rts_out' is '1'. This represents an inactive state assuming a low/'0' active polarity.
24	CTS_POLARITY	RW	RW	0	Polarity of the CTS input signal 'uart_cts_in': '0': CTS is low/'0' active; 'uart_cts_in' is '0' when active and 'uart_cts_in' is '1' when inactive. '1': CTS is high/'1' active; 'uart_cts_in' is '1' when active and 'uart_cts_in' is '0' when inactive.

Bits	Name	SW	HW	Default or Enum	Description
25	CTS_ENABLED	RW	RW	0	Enable use of CTS input signal 'uart_cts_in' by the UART transmitter: '0': Disabled. The UART transmitter ignores 'uart_cts_in', and transmits when a data frame is available for transmission in the TX FIFO or the TX shift register. '1': Enabled. The UART transmitter uses 'uart_cts_in' to qualify the transmission of data. It transmits when 'uart_cts_in' is active and a data frame is available for transmission in the TX FIFO or the TX shift register. If UART_CTRL.LOOPBACK is '1', 'uart_cts_in' is connected to 'uart_rts_out' in the IP (both signals are subjected to signal polarity changes as indicated by RTS_POLARITY and CTS_POLARITY).

24.12.14 SCB_I2C_CTRL

Description: I2C control
Address: 0x40600060
Offset: 0x60
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFB88

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOW_PHASE_OVS [7:4]				HIGH_PHASE_OVS [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	S_NOT_READY_DATA_NACK [15:15]	S_NOT_READY_ADDR_NACK [14:14]	S_READY_DATA_ACK [13:13]	S_READY_ADDR_ACK [12:12]	S_GENERAL_IGNORE [11:11]	None [10:10]	M_NOT_READY_DATA_NACK [9:9]	M_READY_DATA_ACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							LOOPBACK [16:16]

Bits	31	30	29	28	27	26	25	24
Name	MASTER_MODE [31:31]	SLAVE_MODE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	HIGH_PHASE_OVS	RW	RW	8	Serial I2C interface high phase oversampling factor. HIGH_PHASE_OVS + 1 peripheral clock periods constitute the high phase of a bit period. The valid range is [5, 15] with input signal median filtering and [4, 15] without input signal median filtering. The field is only used in master mode. In slave mode, the field is NOT used. However, there is a frequency requirement for the IP clock wrt. the regular interface (IF) high time to guarantee functional correct behavior. With input signal median filtering, the IF high time should be ≥ 6 IP clock cycles and ≤ 16 IP clock cycles. Without input signal median filtering, the IF high time should be ≥ 5 IP clock cycles and ≤ 16 IP clock cycles.

Bits	Name	SW	HW	Default or Enum	Description
4:7	LOW_PHASE_OVS	RW	RW	8	Serial I2C interface low phase oversampling factor. LOW_PHASE_OVS + 1 peripheral clock periods constitute the low phase of a bit period. The valid range is [7, 15] with input signal median filtering and [6, 15] without input signal median filtering. The field is mainly used in master mode. In slave mode, there is a frequency requirement for the IP clock wrt. the regular (no stretching) interface (IF) low time to guarantee functional correct behavior. With input signal median filtering, the IF low time should be ≥ 8 IP clock cycles and ≤ 16 IP clock cycles. Without input signal median filtering, the IF low time should be ≥ 7 IP clock cycles and ≤ 16 IP clock cycles. in slave mode, this field is used to define number of clk_scb cycles for tSU-DAT timing (from ACK/NACK/data ready, to SCL rising edge (released from I2C slave clock stretching))
8	M_READY_DATA_ACK	RW	RW	1	When '1', a received data element by the master is immediately ACK'd when the receiver FIFO is not full.
9	M_NOT_READY_DATA_NACK	RW	RW	1	When '1', a received data element byte the master is immediately NACK'd when the receiver FIFO is full. When '0', clock stretching is used instead (till the receiver FIFO is no longer full).
11	S_GENERAL_IGNORE	RW	RW	1	When '1', a received general call slave address is immediately NACK'd (no ACK or clock stretching) and treated as a non matching slave address. This is useful for slaves that do not need any data supplied within the general call structure.
12	S_READY_ADDR_ACK	RW	RW	1	When '1', a received (matching) slave address is immediately ACK'd when the receiver FIFO is not full. In EZ mode, this field should be set to '1'.
13	S_READY_DATA_ACK	RW	RW	1	When '1', a received data element by the slave is immediately ACK'd when the receiver FIFO is not full. In EZ mode, this field should be set to '1'.

Bits	Name	SW	HW	Default or Enum	Description
14	S_NOT_READY_ADDR_NACK	RW	RW	1	For internally clocked logic (EC_AM is '0' and EC_OP is '0') on an address match or general call address (and S_GENERAL_IGNORE is '0'). Only used when: - EC_AM is '0', EC_OP is '0' and non EZ mode. Functionality is as follows: - 1: a received (matching) slave address is immediately NACK'd when the receiver FIFO is full. - 0: clock stretching is performed (till the receiver FIFO is no longer full). For externally clocked logic (EC_AM is '1') on an address match or general call address (and S_GENERAL_IGNORE is '0'). Only used when (NOT used when EC_AM is '1' and EC_OP is '1' and address match and EZ mode): - EC_AM is '1' and EC_OP is '0'. - EC_AM is '1' and general call address match. - EC_AM is '1' and non EZ mode. Functionality is as follows: - 1: a received (matching or general) slave address is always immediately NACK'd. There are two possibilities: 1). the internally clocked logic is enabled (we are in Active system power mode) and it handles the rest of the current transfer. In this case the I2C master will not observe the NACK. 2). the internally clocked logic is not enabled (we are in DeepSleep system power mode). In this case the I2C master will observe the NACK and may retry the transfer in the future (which gives the internally clocked logic the time to wake up from DeepSleep system power mode). - 0: clock stretching is performed (till the internally clocked logic takes over). The internally clocked logic will handle the ongoing transfer as soon as it is enabled.
15	S_NOT_READY_DATA_NACK	RW	RW	1	For internally clocked logic only. Only used when: - non EZ mode. Functionality is as follows: - 1: a received data element byte the slave is immediately NACK'd when the receiver FIFO is full. - 0: clock stretching is performed (till the receiver FIFO is no longer full).
16	LOOPBACK	RW	RW	0	Local loopback control (does NOT affect the information on the pins). Only applicable in master/slave mode. When '0', the I2C SCL and SDA lines are connected to the I2C SCL and SDA pins. When '1', I2C SCL and SDA lines are routed internally in the peripheral, and as a result unaffected by other I2C devices. This allows a SCB I2C peripheral to address itself.
30	SLAVE_MODE	RW	RW	0	Slave mode enabled ('1') or not ('0').
31	MASTER_MODE	RW	RW	0	Master mode enabled ('1') or not ('0'). Note that both master and slave modes can be enabled at the same time. This allows the IP to address itself.

24.12.15 SCB_I2C_STATUS

Description: I2C status
Address: 0x40600064
Offset: 0x64
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		M_READ [5:5]	S_READ [4:4]	None [3:3]	I2CS_IC_BUSY [2:2]	I2C_EC_BUSY [1:1]	BUS_BUSY [0:0]

Bits	15	14	13	12	11	10	9	8
Name	CURR_EZ_ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BASE_EZ_ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BUS_BUSY	R	R	0	I2C bus is busy. The bus is considered busy ('1'), from the time a START is detected or from the time the SCL line is '0'. The bus is considered idle ('0'), from the time a STOP is detected. If the IP is disabled, BUS_BUSY is '0'. After enabling the IP, it takes time for the BUS_BUSY to detect a busy bus. This time is the maximum high time of the SCL line. For a 100 kHz interface frequency, this maximum high time may last roughly 5 us (half a bit period). For single master systems, BUS_BUSY does not have to be used to detect an idle bus before a master starts a transfer using I2C_M_CMD.M_START (no bus collisions). For multi-master systems, BUS_BUSY can be used to detect an idle bus before a master starts a transfer using I2C_M_CMD.M_START_ON_IDLE (to prevent bus collisions).
1	I2C_EC_BUSY	R	R	Undefined	Indicates whether the externally clocked logic is potentially accessing the EZ memory and/or updating BASE_EZ_ADDR or CURR_EZ_ADDR (this is only possible in EZ mode). This bit can be used by SW to determine whether BASE_EZ_ADDR and CURR_EZ_ADDR are reliable.
2	I2CS_IC_BUSY	R	R	0	Indicates whether the internally clocked slave logic is being accessed by external I2C master. --set at ADDR_MATCH --clear at START/RESET, STOP detection, or BUS_ERROR This bit can be used by SW to determine whether I2CS_IC is busy before entering DeepSleep.

Bits	Name	SW	HW	Default or Enum	Description
4	S_READ	R	R	0	I2C slave read transfer ('1') or I2C slave write transfer ('0'). When the I2C slave is inactive/idle or receiving START, REPEATED START, STOP or an address, this field is '0'.
5	M_READ	R	R	0	I2C master read transfer ('1') or I2C master write transfer ('0'). When the I2C master is inactive/idle or transmitting START, REPEATED START, STOP or an address, this field is '0'.
8:15	CURR_EZ_ADDR	R	R	Undefined	I2C slave current EZ address. Current address pointer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable (during an ongoing transfer when I2C_EC_BUSY is '1'), as clock domain synchronization is not performed in the design.
16:23	BASE_EZ_ADDR	R	R	Undefined	I2C slave base EZ address. Address as provided by an I2C write transfer. This field is only reliable in internally clocked mode. In externally clocked mode the field may be unreliable, as clock domain synchronization is not performed in the design.

24.12.16 SCB_I2C_M_CMD

Description: I2C master command

Address: 0x40600068

Offset: 0x68

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained. This is to ensure that they come up as '0' after coming out of DeepSleep system power mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			M_STOP [4:4]	M_NACK [3:3]	M_ACK [2:2]	M_START _ON_IDLE [1:1]	M_START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	M_START	RW	RW	0	When '1', transmit a START or REPEATED START. Whether a START or REPEATED START is transmitted depends on the state of the master state machine. A START is only transmitted when the master state machine is in the default state. A REPEATED START is transmitted when the master state machine is not in the default state, but is working on an ongoing transaction. The REPEATED START can only be transmitted after a NACK or ACK has been received for a transmitted data element or after a NACK has been transmitted for a received data element. When this action is performed, the hardware sets this field to '0'.
1	M_START_ON_IDLE	RW	RW	0	When '1', transmit a START as soon as the bus is idle (I2C_STATUS.BUS_BUSY is '0', note that BUSY has a default value of '0'). For bus idle detection the hardware relies on STOP detection. As a result, bus idle detection is only functional after at least one I2C bus transfer has been detected on the bus (default/reset value of BUSY is '0'). A START is only transmitted when the master state machine is in the default state. When this action is performed, the hardware sets this field to '0'.
2	M_ACK	RW	RW	0	When '1', attempt to transmit an acknowledgement (ACK). When this action is performed, the hardware sets this field to '0'.
3	M_NACK	RW	RW	0	When '1', attempt to transmit a negative acknowledgement (NACK). When this action is performed, the hardware sets this field to '0'.

Bits	Name	SW	HW	Default or Enum	Description
4	M_STOP	RW	RW	0	When '1', attempt to transmit a STOP. When this action is performed, the hardware sets this field to '0'. I2C_M_CMD.M_START has a higher priority than this command: in situations where both a STOP and a REPEATED START could be transmitted, M_START takes precedence over M_STOP.

24.12.17 SCB_I2C_S_CMD

Description: I2C slave command

Address: 0x4060006C

Offset: 0x6C

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained. This is to ensure that they come up as '0' after coming out of DeepSleep system power mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						S_NACK [1:1]	S_ACK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	S_ACK	RW	RW	0	When '1', attempt to transmit an acknowledgement (ACK). When this action is performed, the hardware sets this field to '0'. In EZ mode, this field should be set to '0' (it is only to be used in non EZ mode).
1	S_NACK	RW	RW	0	When '1', attempt to transmit a negative acknowledgement (NACK). When this action is performed, the hardware sets this field to '0'. In EZ mode, this field should be set to '0' (it is only to be used in non EZ mode). This command has a higher priority than I2C_S_CMD.S_ACK, I2C_CTRL.S_READY_ADDR_ACK or I2C_CTRL.S_READY_DATA_ACK.

24.12.18 SCB_I2C_CFG

Description: I2C configuration

Address: 0x40600070

Offset: 0x70

Retention: Retained

IsDeepSleep: No

Comment: The filters are used to remove glitches and to guarantee I2C compliant SCL and SDA setup and hold times. The filters are trimmable.

Default: 0x2A1013

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SDA_IN_FILT_SEL [4:4]	None [3:2]		SDA_IN_FILT_TRIM [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			SCL_IN_FILT_SEL [12:12]	None [11:10]		SCL_IN_FILT_TRIM [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		SDA_OUT_FILT2_TRIM [21:20]		SDA_OUT_FILT1_TRIM [19:18]		SDA_OUT_FILT0_TRIM [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		SDA_OUT_FILT_SEL [29:28]		None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	SDA_IN_FILT_TRIM	RW	RW	3	Trim bits for 'i2c_sda_in' 50 ns filter. for M0S8 platform, see s8i2cs BROS (001-59539) for more details on the trim bit values. For MXS40 platform, only the Least Significant Bit (LSB) is used, see s40iolib BROS (002-02511) for more details on the trim bit values.
4	SDA_IN_FILT_SEL	RW	RW	1	Selection of 'i2c_sda_in' filter delay: '0': 0 ns. '1': 50 ns (filter enabled).
8:9	SCL_IN_FILT_TRIM	RW	RW	0	Trim bits for 'i2c_scl_in' 50 ns filter. for M0S8 platform, see s8i2cs BROS (001-59539) for more details on the trim bit values. For MXS40 platform, only the Least Significant Bit (LSB) is used, see s40iolib BROS (002-02511) for more details on the trim bit values.
12	SCL_IN_FILT_SEL	RW	RW	1	Selection of 'i2c_scl_in' filter delay: '0': 0 ns. '1': 50 ns (filter enabled).
16:17	SDA_OUT_FILT0_TRIM	RW	RW	2	Trim bits for 'i2c_sda_out' 50 ns filter 0. for M0S8 platform, see s8i2cs BROS (001-59539) for more details on the trim bit values. For MXS40 platform, only the Least Significant Bit (LSB) is used, see s40iolib BROS (002-02511) for more details on the trim bit values.

Bits	Name	SW	HW	Default or Enum	Description
18:19	SDA_OUT_FILT1_TRIM	RW	RW	2	Trim bits for 'i2c_sda_out' 50 ns filter 1. for M0S8 platform, see s8i2cs BROS (001-59539) for more details on the trim bit values. For MXS40 platform, only the Least Significant Bit (LSB) is used, see s40iolib BROS (002-02511) for more details on the trim bit values.
20:21	SDA_OUT_FILT2_TRIM	RW	RW	2	Trim bits for 'i2c_sda_out' 50 ns filter 2. for M0S8 platform, see s8i2cs BROS (001-59539) for more details on the trim bit values. For MXS40 platform, only the Least Significant Bit (LSB) is used, see s40iolib BROS (002-02511) for more details on the trim bit values.
28:29	SDA_OUT_FILT_SEL	RW	RW	0	Selection of cumulative 'i2c_sda_out' filter delay: '0': 0 ns. '1': 50 ns (filter 0 enabled). '2': 100 ns (filters 0 and 1 enabled). '3': 150 ns (filters 0, 1 and 2 enabled).

24.12.19 SCB_TX_CTRL

Description: Transmitter control
Address: 0x40600200
Offset: 0x200
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x107

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			DATA_WIDTH [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							MSB_FIRST [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							OPEN_DRAIN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	DATA_WIDTH	RW	RW	7	Dataframe width. DATA_WIDTH + 1 is the amount of bits in a transmitted data frame. This number does not include start, parity and stop bits. For UART mode, the valid range is [3, 8]. For SPI, the valid range is [3, 31]. For I2C the only valid value is 7.
8	MSB_FIRST	RW	RW	1	Least significant bit first ('0') or most significant bit first ('1'). For I2C, this field should be '1'.

Bits	Name	SW	HW	Default or Enum	Description
16	OPEN_DRAIN	RW	RW	0	Each IO cell 'xxx' has two associated IP output signals 'xxx_out_en' and 'xxx_out'. '0': Normal operation mode. Typically, this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by a single IO cell. In this operation mode, for an IO cell 'xxx' that is used as an output, the 'xxx_out_en' output enable signal is typically constant '1' the 'xxx_out' output is the outputted value. In other words, in normal operation mode, the 'xxx_out' output is used to control the IO cell output value: 'xxx_out' is '0' to drive an IO cell output value of '0' and 'xxx_out' is '1' to drive an IO cell output value of '1'. '1': Open drain operation mode. Typically this operation mode is used for IO cells that are connected to (board) wires/lines that are driven by multiple IO cells (possibly on multiple chips). In this operation mode, for an IO cell 'xxx' that is used as an output, the 'xxx_out_en' output controls the outputted value. Typically, open drain operation mode drives low/'0' and the 'xxx_out' output is constant '1'. In other words, in open drain operation mode, the 'xxx_out_en' output is used to control the IO cell output value: in drive low/'0' mode: 'xxx_out_en' is '1' (drive enabled) to drive an IO cell output value of '0' and 'xxx_out_en' is '1' (drive disabled) to not drive an IO cell output value (another IO cell can drive the wire/line or a pull up results in a wire/line value '1'). The open drain mode is supported for: - UART mode, 'uart_tx' IO cell. - SPI mode, 'spi_miso' IO cell. not applicable to I2C mode, 'i2c_scl' and 'i2c_sda' IO cells. (I2C SCL/SDA always work in open-drain mode)

24.12.20 SCB_TX_FIFO_CTRL

Description: Transmitter FIFO control
Address: 0x40600204
Offset: 0x204
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGGER_LEVEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FREEZE [17:17]	CLEAR [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGGER_LEVEL	RW	RW	0	Trigger level. When the transmitter FIFO has less entries than the number of this field, a transmitter trigger event INTR_TX.TRIGGER is generated.
16	CLEAR	RW	RW	0	When '1', the transmitter FIFO and transmitter shift register are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period.
17	FREEZE	RW	RW	0	When '1', hardware reads from the transmitter FIFO do not remove FIFO entries. Freeze will not advance the TX FIFO read pointer.

24.12.21 SCB_TX_FIFO_STATUS

Description: Transmitter FIFO status
Address: 0x40600208
Offset: 0x208
Retention: Not Retained
IsDeepSleep: No
Comment: This register is not used in EZ and CMD_RESP modes.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	USED [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SR_VALID [15:15]	None [14:9]						USED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RD_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WR_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	USED	R	R	0	Amount of entries in the transmitter FIFO. The value of this field ranges from 0 to FF_DATA_NR (EZ_DATA_NR/2).
15	SR_VALID	R	R	0	Indicates whether the TX shift registers holds a valid data frame ('1') or not ('0'). The shift register can be considered the top of the TX FIFO (the data frame is not included in the USED field of the TX FIFO). The shift register is a working register and holds the data frame that is currently transmitted (when the protocol state machine is transmitting a data frame) or the data frame that is transmitted next (when the protocol state machine is not transmitting a data frame).
16:23	RD_PTR	R	R	0	FIFO read pointer: FIFO location from which a data frame is read by the hardware.
24:31	WR_PTR	R	R	0	FIFO write pointer: FIFO location at which a new data frame is written.

24.12.22 SCB_TX_FIFO_WR

Description: Transmitter FIFO write

Address: 0x40600240

Offset: 0x240

Retention: Not Retained

IsDeepSleep: No

Comment: When the IP is disabled (CTRL.ENABLED is '0') or when the TX FIFO is full, a write to this register is dropped. This register should only be used in FIFO mode (and not in EZ or CMD_RESP modes). This register is 'write only'; a read from this register returns '0'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	W	W	0	Data frame written into the transmitter FIFO. Behavior is similar to that of a PUSH operation. Note that when CTRL.MEM_WIDTH is '0', only DATA[7:0] are used and when CTRL.MEM_WIDTH is '1', only DATA[15:0] are used. A write to a full TX FIFO sets INTR_TX.OVERFLOW to '1'.

24.12.23 SCB_RX_CTRL

Description: Receiver control
Address: 0x40600300
Offset: 0x300
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x107

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			DATA_WIDTH [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						MEDIAN [9:9]	MSB_FIRST [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	DATA_WIDTH	RW	RW	7	Dataframe width. DATA_WIDTH + 1 is the expected amount of bits in received data frame. This number does not include start, parity and stop bits. For UART mode, the valid range is [3, 8]. For SPI, the valid range is [3, 31]. For I2C the only valid value is 7. In EZ mode (for both SPI and I2C), the only valid value is 7.
8	MSB_FIRST	RW	RW	1	Least significant bit first ('0') or most significant bit first ('1'). For I2C, this field should be '1'.
9	MEDIAN	RW	RW	0	Median filter. When '1', a digital 3 taps median filter is performed on input interface lines. This filter should reduce the susceptibility to errors. However, it requires higher oversampling values. For UART IrDA submode, this field should always be '1'.

24.12.24 SCB_RX_FIFO_CTRL

Description: Receiver FIFO control
Address: 0x40600304
Offset: 0x304
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TRIGGER_LEVEL [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FREEZE [17:17]	CLEAR [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TRIGGER_LEVEL	RW	RW	0	Trigger level. When the receiver FIFO has more entries than the number of this field, a receiver trigger event INTR_RX.TRIGGER is generated.
16	CLEAR	RW	RW	0	When '1', the receiver FIFO and receiver shift register are cleared/invalidated. Invalidation will last for as long as this field is '1'. If a quick clear/invalidation is required, the field should be set to '1' and be followed by a set to '0'. If a clear/invalidation is required for an extended time period, the field should be set to '1' during the complete time period.
17	FREEZE	RW	RW	0	When '1', hardware writes to the receiver FIFO have no effect. Freeze will not advance the RX FIFO write pointer.

24.12.25 SCB_RX_FIFO_STATUS

Description: Receiver FIFO status
Address: 0x40600308
Offset: 0x308
Retention: Not Retained
IsDeepSleep: No
Comment: This register is not used in EZ and CMD_RESP modes.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	USED [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	SR_VALID [15:15]	None [14:9]						USED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RD_PTR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	WR_PTR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:8	USED	R	R	0	Amount of entries in the receiver FIFO. The value of this field ranges from 0 to FF_DATA_NR (EZ_DATA_NR/2).
15	SR_VALID	R	R	0	Indicates whether the RX shift registers holds a (partial) valid data frame ('1') or not ('0'). The shift register can be considered the bottom of the RX FIFO (the data frame is not included in the USED field of the RX FIFO). The shift register is a working register and holds the data frame that is currently being received (when the protocol state machine is receiving a data frame).
16:23	RD_PTR	R	R	0	FIFO read pointer: FIFO location from which a data frame is read.
24:31	WR_PTR	R	R	0	FIFO write pointer: FIFO location at which a new data frame is written by the hardware.

24.12.26 SCB_RX_MATCH

Description: Slave address and mask
Address: 0x40600310
Offset: 0x310
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADDR [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MASK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	ADDR	RW	RW	0	Slave device address. In UART multi-processor mode, all 8 bits are used. In I2C slave mode, only bits 7 down to 1 are used. This reflects the organization of the first transmitted byte in a I2C transfer: the first 7 bits represent the address of the addressed slave, and the last 1 bit is a read/write indicator ('0': write, '1': read).
16:23	MASK	RW	RW	0	Slave device address mask. This field is a mask that specifies which of the ADDR field bits in the ADDR field take part in the matching of the slave address: MATCH = ((ADDR & MASK) == ('slave address' & MASK)).

24.12.27 SCB_RX_FIFO_RD

Description: Receiver FIFO read

Address: 0x40600340

Offset: 0x340

Retention: Not Retained

IsDeepSleep: No

Comment: When the IP is disabled (CTRL.ENABLED is '0') or when the RX FIFO is empty, a read from this register returns 0xffff:ffff. This register should only be used in FIFO mode (and not in EZ or CMD_RESP modes). This register is 'read only'; a write to this register is ignored.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Data read from the receiver FIFO. Reading a data frame will remove the data frame from the FIFO; i.e. behavior is similar to that of a POP operation. Note that when CTRL.MEM_WIDTH is '0', only DATA[7:0] are used and when CTRL.MEM_WIDTH is '1', only DATA[15:0] are used. This register has a side effect when read by software: a data frame is removed from the FIFO. This may be undesirable during debug; i.e. a read during debug should NOT have a side effect. To this end, the IP uses the AHB-Lite 'hmaster[0]' input signal. When this signal is '1' in the address cycle of a bus transfer, a read transfer will not have a side effect. As a result, a read from this register will not remove a data frame from the FIFO. As a result, a read from this register behaves as a read from the SCB_RX_FIFO_RD_SILENT register. A read from an empty RX FIFO sets INTR_RX.UNDERFLOW to '1'.

24.12.28 SCB_RX_FIFO_RD_SILENT

Description: Receiver FIFO read silent
Address: 0x40600344
Offset: 0x344
Retention: Not Retained
IsDeepSleep: No
Comment: When the IP is disabled (CTRL.ENABLED is '0') or when the RX FIFO is empty, a read from this register returns 0xffff:ffff. This register should only be used in FIFO mode (and not in EZ or CMD_RESP modes).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA	R	R	Undefined	Data read from the receiver FIFO. Reading a data frame will NOT remove the data frame from the FIFO; i.e. behavior is similar to that of a PEEK operation. Note that when CTRL.MEM_WIDTH is '0', only DATA[7:0] are used and when CTRL.MEM_WIDTH is '1', only DATA[15:0] are used A read from an empty RX FIFO sets INTR_RX.UNDERFLOW to '1'.

24.12.29 SCB_EZ_DATA

Description: Memory buffer

Address: 0x40600400

Offset: 0x400

Retention: Retained

IsDeepSleep: No

Comment: When the IP is disabled (CTRL.ENABLED is '0'), a read from these registers return 0xffff:ffff. It is under MMIO register control whether accesses to this register should introduce bus wait states or be discarded when the externally clocked logic is accessing the memory structure. These registers should only be used in EZ and CMD_RESP modes (and not in FIFO mode).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	EZ_DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	EZ_DATA	RW	RW	Undefined	Data in buffer memory location. In case of a blocked discarded access, a read access returns 0xffff:ffff and a write access is dropped. Note that the 0xffff:ffff value is unique (not a legal EZ_DATA byte value) and can be detected by SW. Note that a discarded write access can be detected by reading back the written value.

24.12.30 SCB_INTR_CAUSE

Description: Active clocked interrupt signal
Address: 0x40600E00
Offset: 0xE00
Retention: Retained
IsDeepSleep: No
Comment: Enables software to determine the source of the combined interrupt output signals 'interrupt_ic', 'interrupt_ec' and 'interrupt'.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		SPI_EC [5:5]	I2C_EC [4:4]	RX [3:3]	TX [2:2]	S [1:1]	M [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	M	R	R	0	Master interrupt active ('interrupt_master'): INTR_M_MASKED != 0.
1	S	R	R	0	Slave interrupt active ('interrupt_slave'): INTR_S_MASKED != 0.
2	TX	R	R	0	Transmitter interrupt active ('interrupt_tx'): INTR_TX_MASKED != 0.
3	RX	R	R	0	Receiver interrupt active ('interrupt_rx'): INTR_RX_MASKED != 0.
4	I2C_EC	R	R	0	Externally clock I2C interrupt active ('interrupt_i2c_ec'): INTR_I2C_EC_MASKED != 0.
5	SPI_EC	R	R	0	Externally clocked SPI interrupt active ('interrupt_spi_ec'): INTR_SPI_EC_MASKED != 0.

24.12.31 SCB_INTR_I2C_EC

Description: Externally clocked I2C interrupt request
Address: 0x40600E80
Offset: 0xE80
Retention: Retained
IsDeepSleep: No
Comment: The fields in this register are set by HW and are cleared by software by writing a '1'. These interrupt causes are generated by externally clocked logic. HW clears the interrupt causes to '0', when the IP is disabled.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	RW1C	RW1C	0	Wake up request. Active on incoming slave request (with address match). Only used when EC_AM is '1'.
1	EZ_STOP	RW1C	RW1C	0	STOP detection. Activated on the end of a every transfer (I2C STOP). Only available for a slave request with an address match, in EZ and CMD_RESP modes, when EC_OP is '1'.
2	EZ_WRITE_STOP	RW1C	RW1C	0	STOP detection after a write transfer occurred. Activated on the end of a write transfer (I2C STOP). This event is an indication that a buffer memory location has been written to. For EZ mode: a transfer that only writes the base address does NOT activate this event. Only available for a slave request with an address match, in EZ and CMD_RESP modes, when EC_OP is '1'.
3	EZ_READ_STOP	RW1C	RW1C	0	STOP detection after a read transfer occurred. Activated on the end of a read transfer (I2C STOP). This event is an indication that a buffer memory location has been read from. Only available for a slave request with an address match, in EZ and CMD_RESP modes, when EC_OP is '1'.

24.12.32 SCB_INTR_I2C_EC_MASK

Description: Externally clocked I2C interrupt mask
Address: 0x40600E88
Offset: 0xE88
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	EZ_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	EZ_WRITE_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
3	EZ_READ_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.33 SCB_INTR_I2C_EC_MASKED

Description: Externally clocked I2C interrupt masked
Address: 0x40600E8C
Offset: 0xE8C
Retention: Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_I2C_EC_MASKED != 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	R	R	0	Logical and of corresponding request and mask bits.
1	EZ_STOP	R	R	0	Logical and of corresponding request and mask bits.
2	EZ_WRITE_STOP	R	R	0	Logical and of corresponding request and mask bits.
3	EZ_READ_STOP	R	R	0	Logical and of corresponding request and mask bits.

24.12.34 SCB_INTR_SPI_EC

Description: Externally clocked SPI interrupt request
Address: 0x40600EC0
Offset: 0xEC0
Retention: Retained
IsDeepSleep: No
Comment: The fields in this register are set by HW and are cleared by software by writing a '1'. These interrupt causes are generated by externally clocked logic. HW clears the interrupt causes to '0', when the IP is disabled.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	RW1C	RW1C	0	Wake up request. Active on incoming slave request when externally clocked selection is '1'. Only used when EC_AM is '1'.
1	EZ_STOP	RW1C	RW1C	0	STOP detection. Activated on the end of a every transfer (SPI deselection). Only available in EZ and CMD_RESP mode and when EC_OP is '1'.
2	EZ_WRITE_STOP	RW1C	RW1C	0	STOP detection after a write transfer occurred. Activated on the end of a write transfer (SPI deselection). This event is an indication that a buffer memory location has been written to. For EZ mode: a transfer that only writes the base address does NOT activate this event. Only used in EZ and CMD_RESP modes and when EC_OP is '1'.
3	EZ_READ_STOP	RW1C	RW1C	0	STOP detection after a read transfer occurred. Activated on the end of a read transfer (SPI deselection). This event is an indication that a buffer memory location has been read from. Only used in EZ and CMD_RESP modes and when EC_OP is '1'.

24.12.35 SCB_INTR_SPI_EC_MASK

Description: Externally clocked SPI interrupt mask
Address: 0x40600EC8
Offset: 0xEC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	EZ_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	EZ_WRITE_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
3	EZ_READ_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.36 SCB_INTR_SPI_EC_MASKED

Description: Externally clocked SPI interrupt masked
Address: 0x40600ECC
Offset: 0xECC
Retention: Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_SPI_EC_MASKED != 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EZ_READ_STOP [3:3]	EZ_WRITE_STOP [2:2]	EZ_STOP [1:1]	WAKE_UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WAKE_UP	R	R	0	Logical and of corresponding request and mask bits.
1	EZ_STOP	R	R	0	Logical and of corresponding request and mask bits.
2	EZ_WRITE_STOP	R	R	0	Logical and of corresponding request and mask bits.
3	EZ_READ_STOP	R	R	0	Logical and of corresponding request and mask bits.

24.12.37 SCB_INTR_M

Description: Master interrupt request

Address: 0x40600F00

Offset: 0xF00

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained in DeepSleep power mode: HW clears the interrupt causes to '0', when coming out of DeepSleep power mode. In addition, HW clears the interrupt causes to '0', when the IP is disabled. As a result, the interrupt causes are only available in Active/Sleep power modes; they are generated by internally clocked logic (this logic operates on a clock that is only available in Active/Sleep power modes).

Default: The interrupt causes should only be used for internally clocked operation; i.e. EC_OP is '0'.
0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			I2C_STOP [4:4]	None [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SPI_DONE [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW1C	RW1C	0	I2C master lost arbitration: the value driven by the master on the SDA line is not the same as the value observed on the SDA line.
1	I2C_NACK	RW1C	RW1C	0	I2C master negative acknowledgement. Set to '1', when the master receives a NACK (typically after the master transmitted the slave address or TX data).
2	I2C_ACK	RW1C	RW1C	0	I2C master acknowledgement. Set to '1', when the master receives a ACK (typically after the master transmitted the slave address or TX data).
4	I2C_STOP	RW1C	RW1C	0	I2C master STOP. Set to '1', when the master has transmitted a STOP.
8	I2C_BUS_ERROR	RW1C	RW1C	0	I2C master bus error (unexpected detection of START or STOP condition).
9	SPI_DONE	RW1C	RW1C	0	SPI master transfer done event: all data frames in the transmit FIFO are sent, the transmit FIFO is empty (both TX FIFO and transmit shifter register are empty), and SPI select output pin is deselected.

24.12.38 SCB_INTR_M_SET

Description: Master interrupt set request
Address: 0x40600F04
Offset: 0xF04
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			I2C_STOP [4:4]	None [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SPI_DONE [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	I2C_NACK	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	I2C_ACK	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
4	I2C_STOP	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	I2C_BUS_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
9	SPI_DONE	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

24.12.39 SCB_INTR_M_MASK

Description: Master interrupt mask
Address: 0x40600F08
Offset: 0xF08
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			I2C_STOP [4:4]	None [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SPI_DONE [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	I2C_NACK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	I2C_ACK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
4	I2C_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	I2C_BUS_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
9	SPI_DONE	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.40 SCB_INTR_M_MASKED

Description: Master interrupt masked request

Address: 0x40600F0C

Offset: 0xF0C

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_M_MASKED != 0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			I2C_STOP [4:4]	None [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SPI_DONE [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	R	R	0	Logical and of corresponding request and mask bits.
1	I2C_NACK	R	R	0	Logical and of corresponding request and mask bits.
2	I2C_ACK	R	R	0	Logical and of corresponding request and mask bits.
4	I2C_STOP	R	R	0	Logical and of corresponding request and mask bits.
8	I2C_BUS_ERROR	R	R	0	Logical and of corresponding request and mask bits.
9	SPI_DONE	R	R	0	Logical and of corresponding request and mask bits.

24.12.41 SCB_INTR_S

Description: Slave interrupt request

Address: 0x40600F40

Offset: 0xF40

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained in DeepSleep power mode: HW clears the interrupt causes to '0', when coming out of DeepSleep power mode. In addition, HW clears the interrupt causes to '0', when the IP is disabled. As a result, the interrupt causes are only available in Active/Sleep power modes; they are generated by internally clocked logic (this logic operates on a clock that is only available in Active/Sleep power modes).

Default: The interrupt causes should only be used for internally clocked operation; i.e. EC_OP is '0'.
0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	I2C_GENERAL [7:7]	I2C_ADDR_MATCH [6:6]	I2C_START [5:5]	I2C_STOP [4:4]	I2C_WRITE_STOP [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				SPI_BUS_ERROR [11:11]	SPI_EZ_STOP [10:10]	SPI_EZ_WRITE_STOP [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW1C	RW1C	0	I2C slave lost arbitration: the value driven on the SDA line is not the same as the value observed on the SDA line (while the SCL line is '1'). This should not occur, it represents erroneous I2C bus behavior. In case of lost arbitration, the I2C slave state machine abort the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error.
1	I2C_NACK	RW1C	RW1C	0	I2C slave negative acknowledgement received. Set to '1', when the slave receives a NACK (typically after the slave transmitted TX data).
2	I2C_ACK	RW1C	RW1C	0	I2C slave acknowledgement received. Set to '1', when the slave receives a ACK (typically after the slave transmitted TX data).

Bits	Name	SW	HW	Default or Enum	Description
3	I2C_WRITE_STOP	RW1C	RW1C	0	I2C STOP event for I2C write transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. In non EZ mode, the event is detected on any I2C write transfer intended for this slave. Note that a I2C write address intended for the slave (address is matching and a it is a write transfer) will result in a I2C_WRITE_STOP event independent of whether the I2C address is ACK'd or NACK'd. In EZ mode, the event is detected only on I2C write transfers that have EZ data written to the memory structure (an I2C write transfer that only communicates an I2C address and EZ address, will not result in this event being detected).
4	I2C_STOP	RW1C	RW1C	0	I2C STOP event for I2C (read or write) transfer intended for this slave (address matching is performed). Set to '1', when STOP or REPEATED START event is detected. The REPEATED START event is included in this interrupt cause such that the I2C transfers separated by a REPEATED START can be distinguished and potentially treated separately by the Firmware. Note that the second I2C transfer (after a REPEATED START) may be to a different slave address. The event is detected on any I2C transfer intended for this slave. Note that a I2C address intended for the slave (address is matching) will result in a I2C_STOP event independent of whether the I2C address is ACK'd or NACK'd.
5	I2C_START	RW1C	RW1C	0	I2C slave START received. Set to '1', when START or REPEATED START event is detected. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') AND clock stretching is performed (till the internally clocked logic takes over) (I2C_CTRL.S_NOT_READY_ADDR_NACK is '0'), this field is NOT set. The Firmware should use INTR_S.EC.WAKE_UP, INTR_S.I2C_ADDR_MATCH and INTR_S.I2C_GENERAL.
6	I2C_ADDR_MATCH	RW1C	RW1C	0	I2C slave matching address received. If CTRL.ADDR_ACCEPT, the received address (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected.
7	I2C_GENERAL	RW1C	RW1C	0	I2C slave general call address received. If CTRL.ADDR_ACCEPT, the received address 0x00 (including the R/W bit) is available in the RX FIFO. In the case of externally clocked address matching (CTRL.EC_AM_MODE is '1') and internally clocked operation (CTRL.EC_OP_MODE is '0'), this field is set when the event is detected.

Bits	Name	SW	HW	Default or Enum	Description
8	I2C_BUS_ERROR	RW1C	RW1C	0	I2C slave bus error (unexpected detection of START or STOP condition). This should not occur, it represents erroneous I2C bus behavior. In case of a bus error, the I2C slave state machine abort the ongoing transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error.
9	SPI_EZ_WRITE_STOP	RW1C	RW1C	0	SPI slave deselected after a write EZ SPI transfer occurred.
10	SPI_EZ_STOP	RW1C	RW1C	0	SPI slave deselected after any EZ SPI transfer occurred.
11	SPI_BUS_ERROR	RW1C	RW1C	0	SPI slave deselected at an unexpected time in the SPI transfer. The Firmware may decide to clear the TX and RX FIFOs in case of this error.

24.12.42 SCB_INTR_S_SET

Description: Slave interrupt set request
Address: 0x40600F44
Offset: 0xF44
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	I2C_GENERAL [7:7]	I2C_ADDR_MATCH [6:6]	I2C_START [5:5]	I2C_STOP [4:4]	I2C_WRITE_STOP [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				SPI_BUS_ERROR [11:11]	SPI_EZ_STOP [10:10]	SPI_EZ_WRITE_STOP [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	I2C_NACK	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	I2C_ACK	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
3	I2C_WRITE_STOP	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
4	I2C_STOP	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
5	I2C_START	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
6	I2C_ADDR_MATCH	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
7	I2C_GENERAL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	I2C_BUS_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
9	SPI_EZ_WRITE_STOP	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
10	SPI_EZ_STOP	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
11	SPI_BUS_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

24.12.43 SCB_INTR_S_MASK

Description: Slave interrupt mask
Address: 0x40600F48
Offset: 0xF48
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	I2C_GENERAL [7:7]	I2C_ADDR_MATCH [6:6]	I2C_START [5:5]	I2C_STOP [4:4]	I2C_WRITE_STOP [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				SPI_BUS_ERROR [11:11]	SPI_EZ_STOP [10:10]	SPI_EZ_WRITE_STOP [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	I2C_NACK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	I2C_ACK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
3	I2C_WRITE_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
4	I2C_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
5	I2C_START	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
6	I2C_ADDR_MATCH	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
7	I2C_GENERAL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	I2C_BUS_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
9	SPI_EZ_WRITE_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
10	SPI_EZ_STOP	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
11	SPI_BUS_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.44 SCB_INTR_S_MASKED

Description: Slave interrupt masked request

Address: 0x40600F4C

Offset: 0xF4C

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_S_MASKED != 0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	I2C_GENERAL [7:7]	I2C_ADDR_MATCH [6:6]	I2C_START [5:5]	I2C_STOP [4:4]	I2C_WRITE_STOP [3:3]	I2C_ACK [2:2]	I2C_NACK [1:1]	I2C_ARB_LOST [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				SPI_BUS_ERROR [11:11]	SPI_EZ_STOP [10:10]	SPI_EZ_WRITE_STOP [9:9]	I2C_BUS_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	I2C_ARB_LOST	R	R	0	Logical and of corresponding request and mask bits.
1	I2C_NACK	R	R	0	Logical and of corresponding request and mask bits.
2	I2C_ACK	R	R	0	Logical and of corresponding request and mask bits.
3	I2C_WRITE_STOP	R	R	0	Logical and of corresponding request and mask bits.
4	I2C_STOP	R	R	0	Logical and of corresponding request and mask bits.
5	I2C_START	R	R	0	Logical and of corresponding request and mask bits.
6	I2C_ADDR_MATCH	R	R	0	Logical and of corresponding request and mask bits.
7	I2C_GENERAL	R	R	0	Logical and of corresponding request and mask bits.
8	I2C_BUS_ERROR	R	R	0	Logical and of corresponding request and mask bits.
9	SPI_EZ_WRITE_STOP	R	R	0	Logical and of corresponding request and mask bits.
10	SPI_EZ_STOP	R	R	0	Logical and of corresponding request and mask bits.
11	SPI_BUS_ERROR	R	R	0	Logical and of corresponding request and mask bits.

24.12.45 SCB_INTR_TX

Description: Transmitter interrupt request

Address: 0x40600F80

Offset: 0xF80

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained In DeepSleep power mode: HW clears the interrupt causes to '0', when coming out of DeepSleep power mode. In addition, HW clears the interrupt causes to '0', when the IP is disabled. As a result, the interrupt causes are only available in Active/Sleep power modes; they are generated by internally clocked logic (this logic operates on a clock that is only available in Active/Sleep power modes).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	EMPTY [4:4]	None [3:2]		NOT_FULL [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					UART_ARB_LOST [10:10]	UART_DONE [9:9]	UART_NACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW1C	RW1C	0	Less entries in the TX FIFO than the value specified by TX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode.
1	NOT_FULL	RW1C	RW1C	0	TX FIFO is not full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is '0': # entries != FF_DATA_NR. MEM_WIDTH is '1': # entries != FF_DATA_NR/2. MEM_WIDTH is '2': # entries != FF_DATA_NR/4. Only used in FIFO mode.
4	EMPTY	RW1C	RW1C	0	TX FIFO is empty; i.e. it has 0 entries. Only used in FIFO mode.
5	OVERFLOW	RW1C	RW1C	0	Attempt to write to a full TX FIFO. Only used in FIFO mode.
6	UNDERFLOW	RW1C	RW1C	0	Attempt to read from an empty TX FIFO. This happens when the IP is ready to transfer data and EMPTY is '1'. Only used in FIFO mode.
7	BLOCKED	RW1C	RW1C	0	AHB-Lite write transfer can not get access to the EZ memory (EZ data access), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'.

Bits	Name	SW	HW	Default or Enum	Description
8	UART_NACK	RW1C	RW1C	0	UART transmitter received a negative acknowledgement in SmartCard mode. Set to '1', when event is detected. Write with '1' to clear bit.
9	UART_DONE	RW1C	RW1C	0	UART transmitter done event. This happens when the IP is done transferring all data in the TX FIFO, and the last stop field is transmitted (both TX FIFO and transmit shifter register are empty). Set to '1', when event is detected. Write with '1' to clear bit.
10	UART_ARB_LOST	RW1C	RW1C	0	UART lost arbitration: the value driven on the TX line is not the same as the value observed on the RX line. This condition event is useful when transmitter and receiver share a TX/RX line. This is the case in LIN or SmartCard modes. Set to '1', when event is detected. Write with '1' to clear bit.

24.12.46 SCB_INTR_TX_SET

Description: Transmitter interrupt set request
Address: 0x40600F84
Offset: 0xF84
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	EMPTY [4:4]	None [3:2]		NOT_FULL [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					UART_ARB_LOST [10:10]	UART_DONE [9:9]	UART_NACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	NOT_FULL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
4	EMPTY	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
5	OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
6	UNDERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
7	BLOCKED	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	UART_NACK	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
9	UART_DONE	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
10	UART_ARB_LOST	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

24.12.47 SCB_INTR_TX_MASK

Description: Transmitter interrupt mask
Address: 0x40600F88
Offset: 0xF88
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	EMPTY [4:4]	None [3:2]		NOT_FULL [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					UART_ARB_LOST [10:10]	UART_DONE [9:9]	UART_NACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	NOT_FULL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
4	EMPTY	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
5	OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
6	UNDERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
7	BLOCKED	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	UART_NACK	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
9	UART_DONE	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
10	UART_ARB_LOST	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.48 SCB_INTR_TX_MASKED

Description: Transmitter interrupt masked request
Address: 0x40600F8C
Offset: 0xF8C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_TX_MASKED != 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	EMPTY [4:4]	None [3:2]		NOT_FULL [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					UART_ARB_LOST [10:10]	UART_DONE [9:9]	UART_NACK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	R	R	0	Logical and of corresponding request and mask bits.
1	NOT_FULL	R	R	0	Logical and of corresponding request and mask bits.
4	EMPTY	R	R	0	Logical and of corresponding request and mask bits.
5	OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
6	UNDERFLOW	R	R	0	Logical and of corresponding request and mask bits.
7	BLOCKED	R	R	0	Logical and of corresponding request and mask bits.
8	UART_NACK	R	R	0	Logical and of corresponding request and mask bits.
9	UART_DONE	R	R	0	Logical and of corresponding request and mask bits.
10	UART_ARB_LOST	R	R	0	Logical and of corresponding request and mask bits.

24.12.49 SCB_INTR_RX

Description: Receiver interrupt request

Address: 0x40600FC0

Offset: 0xFC0

Retention: Not Retained

IsDeepSleep: No

Comment: The register fields are not retained In DeepSleep power mode: HW clears the interrupt causes to '0', when coming out of DeepSleep power mode. In addition, HW clears the interrupt causes to '0', when the IP is disabled. As a result, the interrupt causes are only available in Active/Sleep power modes; they are generated by internally clocked logic (this logic operates on a clock that is only available in Active/Sleep power modes).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	None [4:4]	FULL [3:3]	NOT_EMPTY [2:2]	None [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BREAK_DETECT [11:11]	BAUD_DETECT [10:10]	PARITY_ERROR [9:9]	FRAME_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW1C	RW1C	0	More entries in the RX FIFO than the value specified by RX_FIFO_CTRL.TRIGGER_LEVEL. Only used in FIFO mode.
2	NOT_EMPTY	RW1C	RW1C	0	RX FIFO is not empty. Only used in FIFO mode.
3	FULL	RW1C	RW1C	0	RX FIFO is full. Note that received data frames are lost when the RX FIFO is full. Dependent on CTRL.MEM_WIDTH: (FF_DATA_NR = EZ_DATA_NR/2) MEM_WIDTH is '0': # entries == FF_DATA_NR. MEM_WIDTH is '1': # entries == FF_DATA_NR/2. MEM_WIDTH is '2': # entries == FF_DATA_NR/4. Only used in FIFO mode.
5	OVERFLOW	RW1C	RW1C	0	Attempt to write to a full RX FIFO. Note: in I2C mode, the OVERFLOW is set when a data frame is received and the RX FIFO is full, independent of whether it is ACK'd or NACK'd. Only used in FIFO mode.
6	UNDERFLOW	RW1C	RW1C	0	Attempt to read from an empty RX FIFO. Only used in FIFO mode.

Bits	Name	SW	HW	Default or Enum	Description
7	BLOCKED	RW1C	RW1C	0	AHB-Lite read transfer can not get access to the EZ memory (EZ_DATA accesses), due to an externally clocked EZ access. This may happen when STATUS.EC_BUSY is '1'.
8	FRAME_ERROR	RW1C	RW1C	0	Frame error in received data frame. Set to '1', when event is detected. Write with '1' to clear bit. This can be either a start or stop bit(s) error: Start bit error: after the detection of the beginning of a start bit period (RX line changes from '1' to '0'), the middle of the start bit period is sampled erroneously (RX line is '1'). Note: a start bit error is detected BEFORE a data frame is received. Stop bit error: the RX line is sampled as '0', but a '1' was expected. Note: a stop bit error may result in failure to receive successive data frame(s). Note: a stop bit error is detected AFTER a data frame is received. A stop bit error is detected after a data frame is received, and the UART_RX_CTL.DROP_ON_FRAME_ERROR field specifies whether the received frame is dropped or send to the RX FIFO. If UART_RX_CTL.DROP_ON_FRAME_ERROR is '1', the received data frame is dropped. If UART_RX_CTL.DROP_ON_FRAME_ERROR is '0', the received data frame is send to the RX FIFO. Note that Firmware can only identify the erroneous data frame in the RX FIFO if it is fast enough to read the data frame before the hardware writes a next data frame into the RX FIFO; i.e. the RX FIFO does not have error flags to tag erroneous data frames.
9	PARITY_ERROR	RW1C	RW1C	0	Parity error in received data frame. Set to '1', when event is detected. Write with '1' to clear bit. If UART_RX_CTL.DROP_ON_PARITY_ERROR is '1', the received frame is dropped. If UART_RX_CTL.DROP_ON_PARITY_ERROR is '0', the received frame is send to the RX FIFO. In SmartCard submode, negatively acknowledged data frames generate a parity error. Note that Firmware can only identify the erroneous data frame in the RX FIFO if it is fast enough to read the data frame before the hardware writes a next data frame into the RX FIFO.
10	BAUD_DETECT	RW1C	RW1C	0	LIN baudrate detection is completed. The receiver software uses the UART_RX_STATUS.BR_COUNTER value to set the right IP clock (from the programmable clock IP) to guarantee successful receipt of the first LIN data frame (Protected Identifier Field) after the synchronization byte. Set to '1', when event is detected. Write with '1' to clear bit.

Bits	Name	SW	HW	Default or Enum	Description
11	BREAK_DETECT	RW1C	RW1C	0	Break detection is successful: the line is '0' for UART_RX_CTRL.BREAK_WIDTH + 1 bit period. Can occur at any time to address unanticipated break fields; i.e. 'break-in-data' is supported. This feature is supported for the UART standard and LIN submodes. For the UART standard submodes, ongoing receipt of data frames is NOT affected; i.e. Firmware is expected to take the proper action. For the LIN submode, possible ongoing receipt of a data frame is stopped and the (partially) received data frame is dropped and baud rate detection is started. Set to '1', when event is detected. Write with '1' to clear bit.

24.12.50 SCB_INTR_RX_SET

Description: Receiver interrupt set request
Address: 0x40600FC4
Offset: 0xFC4
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	None [4:4]	FULL [3:3]	NOT_EMPTY [2:2]	None [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BREAK_DETECT [11:11]	BAUD_DETECT [10:10]	PARITY_ERROR [9:9]	FRAME_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	NOT_EMPTY	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
3	FULL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
5	OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
6	UNDERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
7	BLOCKED	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
8	FRAME_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
9	PARITY_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
10	BAUD_DETECT	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.
11	BREAK_DETECT	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt status register.

24.12.51 SCB_INTR_RX_MASK

Description: Receiver interrupt mask
Address: 0x40600FC8
Offset: 0xFC8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	None [4:4]	FULL [3:3]	NOT_EMPTY [2:2]	None [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BREAK_DETECT [11:11]	BAUD_DETECT [10:10]	PARITY_ERROR [9:9]	FRAME_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	NOT_EMPTY	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
3	FULL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
5	OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
6	UNDERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
7	BLOCKED	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	FRAME_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
9	PARITY_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
10	BAUD_DETECT	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
11	BREAK_DETECT	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

24.12.52 SCB_INTR_RX_MASKED

Description: Receiver interrupt masked request

Address: 0x40600FCC

Offset: 0xFCC

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers. This register allows SW to read the status of all mask enabled interrupt causes with a single load operation, rather than two load operations: one for the interrupt causes and one for the masks. This simplifies Firmware development. The associated interrupt is active ('1'), when INTR_RX_MASKED != 0.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKED [7:7]	UNDERFLOW [6:6]	OVERFLOW [5:5]	None [4:4]	FULL [3:3]	NOT_EMPTY [2:2]	None [1:1]	TRIGGER [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BREAK_DETECT [11:11]	BAUD_DETECT [10:10]	PARITY_ERROR [9:9]	FRAME_ERROR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TRIGGER	R	R	0	Logical and of corresponding request and mask bits.
2	NOT_EMPTY	R	R	0	Logical and of corresponding request and mask bits.
3	FULL	R	R	0	Logical and of corresponding request and mask bits.
5	OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
6	UNDERFLOW	R	R	0	Logical and of corresponding request and mask bits.
7	BLOCKED	R	R	0	Logical and of corresponding request and mask bits.
8	FRAME_ERROR	R	R	0	Logical and of corresponding request and mask bits.
9	PARITY_ERROR	R	R	0	Logical and of corresponding request and mask bits.
10	BAUD_DETECT	R	R	0	Logical and of corresponding request and mask bits.
11	BREAK_DETECT	R	R	0	Logical and of corresponding request and mask bits.

25 SDHC

Description	SD/eMMC Host Controller
Base Address	0x40460000
Size	0x10000
Slave Num	MMIO4 - 1

25.1 WRAP

Register Name	Address	Permission	Description
SDHC0_WRAP_CTL	0x40460000	FULL	Top level wrapper control

25.2 CORE

Register Name	Address	Permission	Description
SDHC0_CORE_SDMASA_R	0x40461000	FULL	SDMA System Address register
SDHC0_CORE_BLOCKSIZE_R	0x40461004	FULL	Block Size register
SDHC0_CORE_BLOCKCOUNT_R	0x40461006	FULL	16-bit Block Count register
SDHC0_CORE_ARGUMENT_R	0x40461008	FULL	Argument register
SDHC0_CORE_XFER_MODE_R	0x4046100C	FULL	Transfer Mode register
SDHC0_CORE_CMD_R	0x4046100E	FULL	Command register
SDHC0_CORE_RESP01_R	0x40461010	FULL	Response Register 0/1
SDHC0_CORE_RESP23_R	0x40461014	FULL	Response Register 2/3
SDHC0_CORE_RESP45_R	0x40461018	FULL	Response Register 4/5
SDHC0_CORE_RESP67_R	0x4046101C	FULL	Response Register 6/7
SDHC0_CORE_BUF_DATA_R	0x40461020	FULL	Buffer Data Port Register
SDHC0_CORE_PSTATE_REG	0x40461024	FULL	Present State Register
SDHC0_CORE_HOST_CTRL1_R	0x40461028	FULL	Host Control 1 Register
SDHC0_CORE_PWR_CTRL_R	0x40461029	FULL	Power Control Register
SDHC0_CORE_BGAP_CTRL_R	0x4046102A	FULL	Block Gap Control Register
SDHC0_CORE_WUP_CTRL_R	0x4046102B	FULL	Wakeup Control Register
SDHC0_CORE_CLK_CTRL_R	0x4046102C	FULL	Clock Control Register
SDHC0_CORE_TOUT_CTRL_R	0x4046102E	FULL	Timeout Control Register
SDHC0_CORE_SW_RST_R	0x4046102F	FULL	Software Reset Register
SDHC0_CORE_NORMAL_INT_STAT_R	0x40461030	FULL	Normal Interrupt Status Register
SDHC0_CORE_ERROR_INT_STAT_R	0x40461032	FULL	Error Interrupt Status Register
SDHC0_CORE_NORMAL_INT_STAT_EN_R	0x40461034	FULL	Normal Interrupt Status Enable Register
SDHC0_CORE_ERROR_INT_STAT_EN_R	0x40461036	FULL	Error Interrupt Status Enable Register
SDHC0_CORE_NORMAL_INT_SIGNAL_EN_R	0x40461038	FULL	Normal Interrupt Signal Enable Register
SDHC0_CORE_ERROR_INT_SIGNAL_EN_R	0x4046103A	FULL	Error Interrupt Signal Enable Register
SDHC0_CORE_AUTO_CMD_STAT_R	0x4046103C	FULL	Auto CMD Status Register
SDHC0_CORE_HOST_CTRL2_R	0x4046103E	FULL	Host Control 2 Register
SDHC0_CORE_CAPABILITIES1_R	0x40461040	FULL	Capabilities 1 Register - 0 to 31
SDHC0_CORE_CAPABILITIES2_R	0x40461044	FULL	Capabilities Register - 32 to 63
SDHC0_CORE_CURR_CAPABILITIES1_R	0x40461048	FULL	Current Capabilities Register - 0 to 31
SDHC0_CORE_CURR_CAPABILITIES2_R	0x4046104C	FULL	Maximum Current Capabilities Register - 32 to 63
SDHC0_CORE_FORCE_AUTO_CMD_STAT_R	0x40461050	FULL	Force Event Register for Auto CMD Error Status register
SDHC0_CORE_FORCE_ERROR_INT_STAT_R	0x40461052	FULL	Force Event Register for Error Interrupt Status
SDHC0_CORE_ADMA_ERR_STAT_R	0x40461054	FULL	ADMA Error Status Register
SDHC0_CORE_ADMA_SA_LOW_R	0x40461058	FULL	ADMA System Address Register - Low
SDHC0_CORE_ADMA_ID_LOW_R	0x40461078	FULL	ADMA3 Integrated Descriptor Address Register - Low
SDHC0_CORE_HOST_CNTRL_VERS_R	0x404610FE	FULL	Host Controller Version
SDHC0_CORE_MSHC_VER_ID_R	0x40461500	FULL	MSHC version
SDHC0_CORE_MSHC_VER_TYPE_R	0x40461504	FULL	MSHC version type
SDHC0_CORE_MSHC_CTRL_R	0x40461508	FULL	MSHC Control register
SDHC0_CORE_MBIU_CTRL_R	0x40461510	FULL	MBIU Control register
SDHC0_CORE_EMMC_CTRL_R	0x4046152C	FULL	eMMC Control register Note: CQE_ALGO_SEL CQE_PREFETCH_DISABLE are not available for this register
SDHC0_CORE_BOOT_CTRL_R	0x4046152E	FULL	eMMC Boot Control register
SDHC0_CORE_GP_IN_R	0x40461530	FULL	General Purpose Input register
SDHC0_CORE_GP_OUT_R	0x40461534	FULL	General Purpose Output register

25.3 Register Details

25.3.1 WRAP

25.3.1.1 SDHC_WRAP_CTL

Description: Top level wrapper control
Address: 0x40460000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLE	RW	RW	0	IP Enable: 0: IP disabled, RAM in DeepSleep, SDHC_CORE regs are inaccessible (any attempts to access will result in AHB Error responses), IP is NOT held in reset but the clocks are gated 1: IP enabled, normal operation

25.3.2 CORE

25.3.2.1 SDHC_CORE_SDMASA_R

Description: SDMA System Address register

Address: 0x40461000

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: This register is used to configure a 32-bit Block Count or an SDMA System Address based on the Host Version 4 Enable bit in the Host Control 2 register. This register is applicable for both SD and eMMC modes.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCKCNT_SDMASA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	BLOCKCNT_SDMASA [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	BLOCKCNT_SDMASA [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BLOCKCNT_SDMASA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	BLOCKCNT_SDMA_SA	RW	RW	0	32-bit Block Count (SDMA System Address) - SDMA System Address (Host Version 4 Enable = 0): This register contains the system memory address for an SDMA transfer in the 32-bit addressing mode. When the Host Controller stops an SDMA transfer, this register points to the system address of the next contiguous data position. It can be accessed only if no transaction is executing. Reading this register during data transfers may return an invalid value. - 32-bit Block Count (Host Version 4 Enable = 1): From the Host Controller Version 4.10 specification, this register is redefined as 32-bit Block Count. The Host Controller decrements the block count of this register for every block transfer and the data transfer stops when the count reaches zero. This register must be accessed when no transaction is executing. Reading this register during data transfers may return invalid value. Following are the values for BLOCKCNT_SDMA_SA: - 0xFFFF_FFFF - 4G - 1 Block - - 0x0000_0002 - 2 Blocks - 0x0000_0001 - 1 Block - 0x0000_0000 - Stop Count Note: - When Host Version 4 Enable = 0, SDMA uses this register as system address and hence Auto CMD23 cannot be used with SDMA since this register is assigned for Auto CMD23 as 32-bit Block Count register. - When Host Version 4 Enable = 1, SDMA uses ADMA system address register and this register is reassigned to 32-bit Block Count. This register must be programmed with a non-zero value for data transfer if the 32-bit Block count register is used instead of the 16-bit Block count register. SDMA may use Auto CMD23 if 32-bit Block Count register is used.

25.3.2.2 SDHC_CORE_BLOCKSIZE_R

Description: Block Size register
Address: 0x40461004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: This register is used to configure an SDMA buffer boundary and the number of bytes in a data block. This register is applicable for both SD and eMMC modes.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	XFER_BLOCK_SIZE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	SDMA_BUF_BDARY [14:12]			XFER_BLOCK_SIZE [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:11	XFER_BLOCK_SIZE	RW	RW	0	Transfer Block Size These bits specify the block size of data transfers. In case of memory, it is set to 512 bytes. It can be accessed only if no transaction is executing. Read operations during transfers may return an invalid value, and write operations are ignored. Following are the values for XFER_BLOCK_SIZE: - 0x1: 1 byte - 0x2: 2 bytes - 0x3: 3 bytes - - 0x1FF: 511 byte - 0x200: 512 bytes - - 0x800: 2048 bytes Note: This register must be programmed with a non-zero value for data transfer.

Bits	Name	SW	HW	Default or Enum	Description
12:14	SDMA_BUF_BDARY	RW	RW	0	SDMA Buffer Boundary These bits specify the size of contiguous buffer in system memory. The SDMA transfer waits at every boundary specified by these fields and the Host Controller generates the DMA interrupt to request the Host Driver to update the SDMA System Address register. Values: - 0x0 (BYTES_4K): 4K bytes SDMA Buffer Boundary - 0x1 (BYTES_8K): 8K bytes SDMA Buffer Boundary - 0x2 (BYTES_16K): 16K bytes SDMA Buffer Boundary - 0x3 (BYTES_32K): 32K bytes SDMA Buffer Boundary - 0x4 (BYTES_64K): 64K bytes SDMA Buffer Boundary - 0x5 (BYTES_128K): 128K bytes SDMA Buffer Boundary - 0x6 (BYTES_256K): 256K bytes SDMA Buffer Boundary - 0x7 (BYTES_512K): 512K bytes SDMA Buffer Boundary

25.3.2.3 SDHC_CORE_BLOCKCOUNT_R

Description: 16-bit Block Count register
Address: 0x40461006
Offset: 0x6
Retention: Retained
IsDeepSleep: No
Comment: This register is used to configure the number of data blocks. This register is applicable for both SD and eMMC modes.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BLOCK_CNT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	BLOCK_CNT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	BLOCK_CNT	RW	RW	0	16-bit Block Count - If the Host Version 4 Enable bit is set 0 or the 16-bit Block Count register is set to non-zero, the 16-bit Block Count register is selected. - If the Host Version 4 Enable bit is set 1 and the 16-bit Block Count register is set to zero, the 32-bit Block Count register is selected. Following are the values for BLOCK_CNT: - 0x0: Stop Count - 0x1: 1 Block - 0x2: 2 Blocks - ... - ... - 0xFFFF: 65535 Blocks Note: For Host Version 4 Enable = 0, this register must be set to 0000h before programming the 32-bit block count register when Auto CMD23 is enabled for non-DMA and ADMA modes.

25.3.2.4 SDHC_CORE_ARGUMENT_R

Description: Argument register
Address: 0x40461008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: This register is used to configure the SD/eMMC command argument.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ARGUMENT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ARGUMENT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ARGUMENT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ARGUMENT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ARGUMENT	RW	RW	0	Command Argument These bits specify the SD/eMMC command argument that is specified in bits 39-8 of the Command format.

25.3.2.5 SDHC_CORE_XFER_MODE_R

Description: Transfer Mode register
Address: 0x4046100C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control the operation of data transfers for an SD/eMMC mode. The Host driver sets this register before issuing a command that transfers data.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESP_ERR_CHK_ENABLE [7:7]	RESP_TYPE [6:6]	MULTI_BLK_SEL [5:5]	DATA_XFER_DIR [4:4]	AUTO_CMD_ENABLE [3:2]	BLOCK_COUNT_ENABLE [1:1]	DMA_ENABLE [0:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							RESP_INT_DISABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DMA_ENABLE	RW	RW	0	DMA Enable This bit enables the DMA functionality. If this bit is set to 1, a DMA operation begins when the Host Driver writes to the Command register. You can select one of the DMA modes by using DMA Select in the Host Control 1 register. Values: - 0x1 (ENABLED): DMA Data transfer - 0x0 (DISABLED): No data transfer or Non-DMA data transfer
1	BLOCK_COUNT_ENABLE	RW	RW	0	Block Count Enable This bit is used to enable the Block Count register, which is relevant for multiple block transfers. If this bit is set to 0, the Block Count register is disabled, which is useful in executing an infinite transfer. The Host Driver must set this bit to 0 when ADMA is used. When 16-bit Block Count register is used, the Host Driver can set this bit to 0 in ADMA2 mode to enable larger data transfer than the maximum of 65535 block counts supported by the 16-bit Block Count register.

Bits	Name	SW	HW	Default or Enum	Description
2:3	AUTO_CMD_ENABLE	RW	RW	0	Auto Command Enable This field determines use of Auto Command functions. Note: In SDIO, this field must be set as 00b (Auto Command Disabled). Values: - 0x0 (AUTO_CMD_DISABLED): Auto Command Disabled - 0x1 (AUTO_CMD12_ENABLED): Auto CMD12 Enable - 0x2 (AUTO_CMD23_ENABLED): Auto CMD23 Enable - 0x3 (AUTO_CMD_AUTO_SEL): Auto CMD Auto Select
4	DATA_XFER_DIR	RW	RW	0	Data Transfer Direction Select This bit defines the direction of DAT line data transfers. This bit is set to 1 by the Host Driver to transfer data from the SD/eMMC card to the Host Controller and it is set to 0 for all other commands. Values: - 0x1 (READ): Read (Card to Host) - 0x0 (WRITE): Write (Host to Card)
5	MULTI_BLK_SEL	RW	RW	0	Multi/Single Block Select This bit is set when issuing multiple-block transfer commands using the DAT line. If this bit is set to 0, it is not necessary to set the Block Count register.
6	RESP_TYPE	RW	RW	0	Response Type R1/R5 This bit selects either R1 or R5 as a response type when the Response Error Check is selected. Error statuses checked in R1: - OUT_OF_RANGE - ADDRESS_ERROR - BLOCK_LEN_ERROR - WP_VIOLATION - CARD_IS_LOCKED - COM_CRC_ERROR - CARD_ECC_FAILED - CC_ERROR - ERROR Response Flags checked in R5: - COM_CRC_ERROR - ERROR - FUNCTION_NUMBER - OUT_OF_RANGE Values: - 0x0 (RESP_R1): R1 (Memory) - 0x1 (RESP_R5): R5 (SDIO)

Bits	Name	SW	HW	Default or Enum	Description
7	RESP_ERR_CHK_ENABLE	RW	RW	0	Response Error Check Enable The Host Controller supports response check function to avoid overhead of response error check by Host driver. Response types of only R1 and R5 can be checked by the Controller. If the Host Controller checks the response error, set this bit to 1 and set Response Interrupt Disable to 1. If an error is detected, the Response Error interrupt is generated in the Error Interrupt Status register. Note: - Response error check must not be enabled for any response type other than R1 and R5. Values: - 0x0 (DISABLED): Response Error Check is disabled - 0x1 (ENABLED): Response Error Check is enabled
8	RESP_INT_DISABLE	RW	RW	0	Response Interrupt Disable The Host Controller supports response check function to avoid overhead of response error check by the Host driver. Response types of only R1 and R5 can be checked by the Controller. If Host Driver checks the response error, set this bit to 0 and wait for Command Complete Interrupt and then check the response register. If the Host Controller checks the response error, set this bit to 1 and set the Response Error Check Enable bit to 1. The Command Complete Interrupt is disabled by this bit regardless of the Command Complete Signal Enable. Values: - 0x0 (ENABLED): Response Interrupt is enabled - 0x1 (DISABLED): Response Interrupt is disabled

25.3.2.6 SDHC_CORE_CMD_R

Description: Command register
Address: 0x4046100E
Offset: 0xE
Retention: Retained
IsDeepSleep: No
Comment: This register is used to provide the information related to a command and a response packet. This register is applicable for an SD/eMMC mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CMD_TYPE [7:6]		DATA _PRESENT _SEL [5:5]	CMD_IDX _CHK _ENABLE [4:4]	CMD_CRC _CHK _ENABLE [3:3]	SUB_CMD _FLAG [2:2]	RESP_TYPE_SELECT [1:0]	
Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		CMD_INDEX [13:8]					
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	RESP_TYPE_SELECT	RW	RW	0	Response Type Select This bit indicates the type of response expected from the card. Values: - 0x0 (NO_RESP): No Response - 0x1 (RESP_LEN_136): Response Length 136 - 0x2 (RESP_LEN_48): Response Length 48 - 0x3 (RESP_LEN_48B): Response Length 48; Check Busy after response
2	SUB_CMD_FLAG	RW	RW	0	Sub Command Flag This bit distinguishes between a main command and a sub command. Values: - 0x0 (MAIN): Main Command - 0x1 (SUB): Sub Command
3	CMD_CRC_CHK_ENABLE	RW	RW	0	Command CRC Check Enable This bit enables the Host Controller to check the CRC field in the response. If an error is detected, it is reported as a Command CRC error. Note: - CRC Check enable must be set to 0 for the command with no response, R3 response, and R4 response. Values: - 0x0 (DISABLED): Disable - 0x1 (ENABLED): Enable

Bits	Name	SW	HW	Default or Enum	Description
4	CMD_IDX_CHK_ENABLE	RW	RW	0	Command Index Check Enable This bit enables the Host Controller to check the index field in the response to verify if it has the same value as the command index. If the value is not the same, it is reported as a Command Index error. Note: - Index Check enable must be set to 0 for the command with no response, R2 response, R3 response and R4 response. Values: - 0x0 (DISABLED): Disable - 0x1 (ENABLED): Enable
5	DATA_PRESENT_SEL	RW	RW	0	Data Present Select This bit is set to 1 to indicate that data is present and that the data is transferred using the DAT line. This bit is set to 0 in the following instances: - Command using the CMD line - Command with no data transfer but using busy signal on the DAT[0] line - Resume Command Values: - 0x0 (NO_DATA): No Data Present - 0x1 (DATA): Data Present
6:7	CMD_TYPE	RW	RW	0	Command Type These bits indicate the command type. Note: While issuing Abort CMD using CMD12/CMD52 or reset CMD using CMD0/CMD52, CMD_TYPE field shall be set to 0x3. Values: - 0x3 (ABORT_CMD): Abort - 0x2 (RESUME_CMD): Resume - 0x1 (SUSPEND_CMD): Suspend - 0x0 (NORMAL_CMD): Normal
8:13	CMD_INDEX	RW	RW	0	Command Index These bits are set to the command number that is specified in bits 45-40 of the Command Format.

25.3.2.7 SDHC_CORE_RESP01_R

Description: Response Register 0/1

Address: 0x40461010

Offset: 0x10

Retention: Retained

IsDeepSleep: No

Comment: This register stores 39-08 bits of the Response Field for an SD/eMMC mode. In UHS-II mode, this register stores the response of the TRANS_ABORT CCMD. The response for an SD/eMMC command can be a maximum of 128 bits. These 128 bits are segregated into four 32-bit registers: RESP01_R, RESP23_R, RESP45_R and RESP67_R.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESP01 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	RESP01 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	RESP01 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	RESP01 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESP01	R	R	0	Command Response These bits reflect 39-8 bits of SD/eMMC Response Field. Note: For Auto CMD, the 32-bit response (bits 39-8 of the Response Field) is updated in the RESP67_R register.

25.3.2.8 SDHC_CORE_RESP23_R

Description: Response Register 2/3

Address: 0x40461014

Offset: 0x14

Retention: Retained

IsDeepSleep: No

Comment: This register stores 71-40 bits of the Response Field for an SD/eMMC mode. This register is used to store the response from the cards. The response can be a maximum of 128 bits.

These 128 bits are segregated into four 32-bit registers: RESP01_R, RESP23_R, RESP45_R and RESP67_R. In UHS-II mode, this register is reserved

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESP23 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESP23 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESP23 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESP23 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESP23	R	R	0	Command Response These bits reflect 71-40 bits of the SD/eMMC Response

25.3.2.9 SDHC_CORE_RESP45_R

Description: Response Register 4/5

Address: 0x40461018

Offset: 0x18

Retention: Retained

IsDeepSleep: No

Comment: This register stores 103-72 bits of the Response Field for an SD/eMMC mode. In UHS-II mode, this register is used to store the lower 4-byte CMD12 response. The response for SD/eMMC

command can be a maximum of 128 bits. These 128 bits are segregated into four 32-bit registers:

RESP01_R, RESP23_R, RESP45_R and RESP67_R.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESP45 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	RESP45 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RESP45 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	RESP45 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESP45	R	R	0	Command Response These bits reflect 103-72 bits of the Response Field.

25.3.2.10 SDHC_CORE_RESP67_R

Description: Response Register 6/7

Address: 0x4046101C

Offset: 0x1C

Retention: Retained

IsDeepSleep: No

Comment: This register stores 135-104 bits of the Response Field for an SD/eMMC mode. In UHSII mode, this register stores the upper 4-byte CMD12 response. The SD/eMMC response can be a maximum of 128 bits. These 128 bits are segregated into four 32-bit registers: RESP01_R, RESP23_R, RESP45_R and RESP67_R.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESP67 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	RESP67 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	RESP67 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	RESP67 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	RESP67	R	R	0	Command Response These bits reflect bits 135-104 of SD/EMMC Response Field. Note: For Auto CMD, this register also reflects the 32-bit response (bits 39-8 of the Response Field).

25.3.2.11 SDHC_CORE_BUF_DATA_R

Description: Buffer Data Port Register
Address: 0x40461020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: This register is used to access the packet buffer. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BUF_DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	BUF_DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	BUF_DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	BUF_DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	BUF_DATA	RW	RW	0	Buffer Data These bits enable access to the Host Controller packet buffer.

Bits	Name	SW	HW	Default or Enum	Description
1	CMD_INHIBIT_DAT	R	R	0	Command Inhibit (DAT) This bit is applicable for SD/eMMC mode and is generated if either DAT line active or Read transfer active is set to 1. If this bit is set to 0, it indicates that the Host Controller can issue subsequent SD/eMMC commands. Values: - 0x0 (READY): Can issue command which used DAT line - 0x1 (NOT_READY): Cannot issue command which used DAT line
2	DAT_LINE_ACTIVE	R	R	0	DAT Line Active (SD/eMMC Mode only) This bit indicates whether one of the DAT lines on the SD/eMMC bus is in use. In the case of read transactions, this bit indicates whether a read transfer is executing on the SD/eMMC bus. In the case of write transactions, this bit indicates whether a write transfer is executing on the SD/eMMC bus. For a command with busy, this status indicates whether the command executing busy is executing on an SD or eMMC bus. Values: - 0x0 (INACTIVE): DAT Line Inactive - 0x1 (ACTIVE): DAT Line Active
4:7	DAT_7_4	R	R	0	DAT[7:4] Line Signal Level This bit is used to check the DAT line level to recover from errors and for debugging. These bits reflect the value of the sd_dat_in (upper nibble) signal.
8	WR_XFER_ACTIVE	R	R	0	Write Transfer Active This status indicates whether a write transfer is active for SD/eMMC mode. Values: - 0x0 (INACTIVE): No valid data - 0x1 (ACTIVE): Transferring data
9	RD_XFER_ACTIVE	R	R	0	Read Transfer Active This bit indicates whether a read transfer is active for SD/eMMC mode. Values: - 0x0 (INACTIVE): No valid data - 0x1 (ACTIVE): Transferring data
10	BUF_WR_ENABLE	R	R	0	Buffer Write Enable This bit is used for non-DMA transfers. This bit is set if space is available for writing data. Values: - 0x0 (DISABLED): Write disable - 0x1 (ENABLED): Write enable

Bits	Name	SW	HW	Default or Enum	Description
11	BUF_RD_ENABLE	R	R	0	Buffer Read Enable This bit is used for non-DMA transfers. This bit is set if valid data exists in the Host buffer. Values: - 0x0 (DISABLED): Read disable - 0x1 (ENABLED): Read enable
16	CARD_INSERTED	R	R	0	Card Inserted This bit indicates whether a card has been inserted. The Host Controller debounces this signal so that Host Driver need not wait for it to stabilize. Values: - 0x0 (FALSE): Reset, Debouncing, or No card - 0x1 (TRUE): Card Inserted
17	CARD_STABLE	R	R	0	Card Stable This bit indicates the stability of the Card Detect Pin Level. A card is not detected if this bit is set to 1 and the value of the CARD_INSERTED bit is 0. Values: - 0x0 (FALSE): Reset or Debouncing - 0x1 (TRUE): No Card or Inserted
18	CARD_DETECT_PIN_LEVEL	R	R	0	Card Detect Pin Level This bit reflects the inverse synchronized value of the card_detect_n signal. Values: - 0x0 (FALSE): No card present - 0x1 (TRUE): Card Present
19	WR_PROTECT_SW_LVL	R	R	0	Write Protect Switch Pin Level This bit is supported only for memory and combo cards. This bit reflects the synchronized value of the card_write_prot signal. Values: - 0x0 (FALSE): Write protected - 0x1 (TRUE): Write enabled
20:23	DAT_3_0	R	R	0	DAT[3:0] Line Signal Level This bit is used to check the DAT line level to recover from errors and for debugging. These bits reflect the value of the sd_dat_in (lower nibble) signal.
24	CMD_LINE_LVL	R	R	0	Command-Line Signal Level This bit is used to check the CMD line level to recover from errors and for debugging. These bits reflect the value of the sd_cmd_in signal.
25	HOST_REG_VOL	R	R	0	Host Regulator Voltage Stable This bit is used to check whether the host regulator voltage is stable for switching the voltage of UHS-I mode. This bit reflects the synchronized value of the host_reg_vol_stable signal. Values: - 0x0 (FALSE): Host Regulator Voltage is not stable - 0x1 (TRUE): Host Regulator Voltage is stable

Bits	Name	SW	HW	Default or Enum	Description
27	CMD_ISSU_ERR	R	R	0	Command Not Issued by Error This bit is set if a command cannot be issued after setting the command register due to an error except the Auto CMD12 error. Values: - 0x0 (FALSE): No error for issuing a command - 0x1 (TRUE): Command cannot be issued
28	SUB_CMD_STAT	R	R	0	Sub Command Status This bit is used to distinguish between a main command and a sub command status. Values: - 0x0 (FALSE): Main Command Status - 0x1 (TRUE): Sub Command Status

25.3.2.13 SDHC_CORE_HOST_CTRL1_R

Description: Host Control 1 Register
Address: 0x40461028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control the operation of the Host Controller. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CARD_DETECT_SIG_SEL [7:7]	CARD_DETECT_TEST_LVL [6:6]	EXT_DAT_XFER [5:5]	DMA_SEL [4:3]		HIGH_SPEED_EN [2:2]	DAT_XFER_WIDTH [1:1]	LED_CTRL [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LED_CTRL	RW	RW	0	LED Control This bit is used to caution the user not to remove the card while the SD card is being accessed. The value is reflected on the led_ctrl output. Values: - 0x0 (OFF): LED off - 0x1 (ON): LED on
1	DAT_XFER_WIDTH	RW	RW	0	Data Transfer Width For SD/eMMC mode, this bit selects the data transfer width of the Host Controller. The Host Driver sets it to match the data width of the SD/eMMC card. Values: - 0x1 (FOUR_BIT): 4-bit mode - 0x0 (ONE_BIT): 1-bit mode
2	HIGH_SPEED_EN	RW	RW	0	High Speed Enable (SD/eMMC Mode only) Before setting this bit, the Host Driver checks the High Speed Support in the Capabilities register. Note: SDHC always outputs the sd_cmd_out and sd_dat_out lines at the rising edge of card clock irrespective of this bit. Values: - 0x1 (HIGH_SPEED): High Speed mode - 0x0 (NORMAL_SPEED): Normal Speed mode

Bits	Name	SW	HW	Default or Enum	Description
3:4	DMA_SEL	RW	RW	0	DMA Select This field is used to select the DMA type. When Host Version 4 Enable is 1 in Host Control 2 register: - 0x0 - SDMA is selected - 0x1 - Reserved - 0x2 - ADMA2 is selected - 0x3 - ADMA2 or ADMA3 is selected When Host Version 4 Enable is 0 in Host Control 2 register: - 0x0 - SDMA is selected - 0x1 - Reserved - 0x2 - 32-bit Address ADMA2 is selected - 0x3 - Reserved Values: - 0x0 (SDMA): SDMA is selected - 0x1 (RSVD_BIT): Reserved - 0x2 (ADMA2): ADMA2 is selected - 0x3 (ADMA2_3): ADMA2 or ADMA3 is selected
5	EXT_DAT_XFER	RW	RW	0	Extended Data Transfer Width This bit controls 8-bit bus width mode of embedded device. Values: - 0x1 (EIGHT_BIT): 8-bit Bus Width - 0x0 (DEFAULT): Bus Width is selected by the Data Transfer Width
6	CARD_DETECT_TEST_LVL	RW	RW	0	Card Detect Test Level This bit is enabled while the Card Detect Signal Selection is set to 1 and it indicates whether a card inserted or not. Values: - 0x1 (CARD_INSERTED): Card Inserted - 0x0 (No_CARD): No Card
7	CARD_DETECT_SIG_SEL	RW	RW	0	Card Detect Signal Selection This bit selects a source for card detection. When the source for the card detection is switched, the interrupt must be disabled during the switching period. Values: - 0x1 (CARD_DT_TEST_LEVEL): Card Detect Test Level is selected (for test purpose) - 0x0 (card_detect_n): card_detect_n signal is selected (for normal use)

25.3.2.14 SDHC_CORE_PWR_CTRL_R

Description: Power Control Register

Address: 0x40461029

Offset: 0x29

Retention: Retained

IsDeepSleep: No

Comment: This register is used to control the bus power for the Card. This register is applicable for an SD, eMMC, and UHS-II modes.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				SD_BUS_VOL_VDD1 [3:1]			SD_BUS_PWR_VDD1 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SD_BUS_PWR_VDD1	RW	RW	0	SD Bus Power for VDD1 This bit enables VDD1 power of the card. This setting is available on the card_if_pwr_en output so that it can be used to control the VDD1 power supply of the card. Before setting this bit, the SD Host Driver sets the SD Bus Voltage Select bit. If the Host Controller detects a No Card state, this bit is cleared. In SD mode, if this bit is cleared, the Host Controller stops the SD Clock by clearing the SD_CLK_IN bit in the CLK_CTRL_R register. Values: - 0x0 (OFF): Power off - 0x1 (ON): Power on
1:3	SD_BUS_VOL_VDD1	RW	RW	0	These bits are NON-operational (they can be written and read but they have no effect). In a generic HCI host these would select the card supply voltage. But, for the applications targeted for this block it is assumed that the card supply voltage is always fixed at the board level. If for some reason there is a variable power supply then that can be managed through normal GPIO programming separately.

25.3.2.15 SDHC_CORE_BGAP_CTRL_R

Description: Block Gap Control Register
Address: 0x4046102A
Offset: 0x2A
Retention: Retained
IsDeepSleep: No
Comment: This register is used by the host driver to control any operation related to Block Gap.
 This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				INT_AT_BG AP [3:3]	RD_WAIT _CTRL [2:2]	CONTINUE _REQ [1:1]	STOP_BG _REQ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	STOP_BG_REQ	RW	RW	0	Stop At Block Gap Request This bit is used to stop executing read and write transactions at the next block gap for non-DMA, SDMA, and ADMA transfers. Values: - 0x0 (XFER): Transfer - 0x1 (STOP): Stop
1	CONTINUE_REQ	RW	RW	0	Continue Request This bit is used to restart the transaction, which was stopped using the Stop At Block Gap Request. The Host Controller automatically clears this bit when the transaction restarts. If stop at block gap request is set to 1, any write to this bit is ignored. Values: - 0x0 (NO_AFFECT): No Affect - 0x1 (RESTART): Restart
2	RD_WAIT_CTRL	RW	RW	0	Reserved: set to 0
3	INT_AT_BGAP	RW	RW	0	Interrupt At Block Gap This bit is valid only in the 4-bit mode of an SDIO card and is used to select a sample point in the interrupt cycle. Setting to 1 enables interrupt detection at the block gap for a multiple block transfer. Values: - 0x0 (DISABLE): Disabled - 0x1 (ENABLE): Enabled

25.3.2.16 SDHC_CORE_WUP_CTRL_R

Description: Wakeup Control Register

Address: 0x4046102B

Offset: 0x2B

Retention: Retained

IsDeepSleep: No

Comment: The intention of this 'wakeup' register is to wake up an otherwise idle Host driver. It is NOT a wake up from DeepSleep. clk_peri must be running in order for the events below to be detected and reported. All other clocks to the block can be gated, though. Note that the Host Driver must maintain voltage on the SD Bus by setting the SD Bus Power to 1 in the Power Control Register if a wakeup event through the Card Interrupt is desired.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					WUP_CARD_REMOVAL [2:2]	WUP_CARD_INSERT [1:1]	WUP_CARD_INT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WUP_CARD_INT	RW	RW	0	Wakeup Event Enable on SDIO Card Interrupt (through DAT[1]). This bit enables wakeup event through an SDIO Card Interrupt assertion in the Normal Interrupt Status register. This bit can be set to 1 if FN_WUS (Wake Up Support) in CIS is set to 1. Values: - 0x0 (DISABLED): Disable - 0x1 (ENABLED): Enable
1	WUP_CARD_INSERT	RW	RW	0	Wakeup Event Enable on SD Card Insertion This bit enables wakeup event through Card Insertion assertion in the Normal Interrupt Status register. FN_WUS (Wake Up Support) in CIS does not affect this bit. Values: - 0x0 (DISABLED): Disable - 0x1 (ENABLED): Enable
2	WUP_CARD_REMOVAL	RW	RW	0	Wakeup Event Enable on SD Card Removal This bit enables wakeup event through Card Removal assertion in the Normal Interrupt Status register. For the SDIO card, Wake Up Support (FN_WUS) in the Card Information Structure (CIS) register does not affect this bit. Values: - 0x0 (DISABLED): Disable - 0x1 (ENABLED): Enable

25.3.2.17 SDHC_CORE_CLK_CTRL_R

Description: Clock Control Register
Address: 0x4046102C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment: This register controls SDCLK (card clock) in an SD/eMMC mode and RCLK in the UHS-II mode. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UPPER_FREQ_SEL [7:6]		CLK_GEN_SELECT [5:5]	None [4:4]	PLL_ENABLE [3:3]	SD_CLK_EN [2:2]	INTERNAL_CLK_STABLE [1:1]	INTERNAL_CLK_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	FREQ_SEL [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INTERNAL_CLK_EN	RW	RW	0	Internal Clock Enable This bit is set to 0 when the Host Driver is not using the Host Controller or the Host Controller awaits a wakeup interrupt. The Host Controller must stop its internal clock to enter a very low power state. Certain registers are not accessible when this bit is off. So, to be safe turn it on for any register access. Values: - 0x0 (FALSE): Stop - 0x1 (TRUE): Oscillate
1	INTERNAL_CLK_STABLE	R	R	0	Internal Clock Stable This bit enables the Host Driver to check the clock stability twice after the Internal Clock Enable bit is set and after the PLL Enable bit is set. This bit reflects the synchronized value of the Internal Clock Stable signal after the Internal Clock Enable bit is set to 1 and also reflects the synchronized value of the Card Clock Stable signal after the PLL Enable bit is set to 1. Values: - 0x0 (FALSE): Not Ready - 0x1 (TRUE): Ready

Bits	Name	SW	HW	Default or Enum	Description
2	SD_CLK_EN	RW	RW	0	SD/eMMC Clock Enable This bit stops the clk_card output when set to 0. The SDCLK Frequency Select bit can be changed when this bit is set to 0. Values: - 0x0 (FALSE): Disable providing clk_card - 0x1 (TRUE): Enable providing clk_card
3	PLL_ENABLE	RW	RW	0	PLL Enable This bit is used to activate the PLL (applicable when Host Version 4 Enable = 1). Values: - 0x0 (FALSE): PLL is in low power mode - 0x1 (TRUE): PLL is enabled
5	CLK_GEN_SELECT	RW	RW	0	Clock Generator Select This bit is used to select the clock generator mode in SDCLK Frequency Select. Values: - 0x0 (FALSE): Divided Clock Mode - 0x1 (TRUE): Programmable Clock Mode
6:7	UPPER_FREQ_SEL	RW	RW	0	These bits specify the upper 2 bits of 10-bit SDCLK Frequency Select control.
8:15	FREQ_SEL	RW	RW	0	SDCLK Frequency Select These bits are used to select the frequency of the SDCLK signal. 10-bit Divided Clock Mode: - 0x3FF - 1/2046 Divided clock - - N - 1/2N Divided Clock - - 0x002 - 1/4 Divided Clock - 0x001 - 1/2 Divided Clock - 0x000 - Base clock (10MHz - 255 MHz)

25.3.2.18 SDHC_CORE_TOUT_CTRL_R

Description: Timeout Control Register
Address: 0x4046102E
Offset: 0x2E
Retention: Retained
IsDeepSleep: No
Comment: This register is used to set the Data Timeout Counter value for an SD/eMMC mode according to the timer clock defined by the Capabilities register, while initializing the Host Controller.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				TOUT_CNT [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	TOUT_CNT	RW	RW	0	Data Timeout Counter Value. This value determines the interval by which DAT line timeouts are detected. The Timeout clock frequency is generated by dividing the base clock TMCLK value by this value. When setting this register, prevent inadvertent timeout events by clearing the Data Timeout Error Status Enable (in the Error Interrupt Status Enable register). The values for these bits are: - 0xF - Reserved - 0xE - $TMCLK \times 2^{27}$ - - 0x1 - $TMCLK \times 2^{14}$ - 0x0 - $TMCLK \times 2^{13}$ Note: During a boot operating in an eMMC mode, an application must configure the boot data timeout value (approximately 1 sec) in this bit.

25.3.2.19 SDHC_CORE_SW_RST_R

Description: Software Reset Register

Address: 0x4046102F

Offset: 0x2F

Retention: Retained

IsDeepSleep: No

Comment: This register is used to generate a reset pulse by writing 1 to each bit of this register. After completing the reset, the Host Controller clears each bit. As it takes some time to complete a software reset, the Host Driver confirms that these bits are 0. This register is applicable for an SD/eMMC/UHS-II mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					SW_RST_DAT [2:2]	SW_RST_CMD [1:1]	SW_RST_ALL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SW_RST_ALL	RW	RW	0	Software Reset For All This reset affects the entire Host Controller except for the card detection circuit. During its initialization, the Host Driver sets this bit to 1 to reset the Host Controller. All registers are reset except the capabilities register. If this bit is set to 1, the Host Driver must issue reset command and reinitialize the card. Values: - 0x0 (FALSE): Work - 0x1 (TRUE): Reset

Bits	Name	SW	HW	Default or Enum	Description
1	SW_RST_CMD	RW	RW	0	Software Reset For CMD line This bit resets only a part of the command circuit to be able to issue a command. This reset is effective only for a command issuing circuit (including response error statuses related to Command Inhibit (CMD) control) and does not affect the data transfer circuit. Host Controller can continue data transfer even after this reset is executed while handling subcommand-response errors. The following registers and bits are cleared by this bit: - Present State register - Command Inhibit (CMD) bit - Normal Interrupt Status register - Command Complete bit - Error Interrupt Status - Response error statuses related to Command Inhibit (CMD) bit Values: - 0x0 (FALSE): Work - 0x1 (TRUE): Reset
2	SW_RST_DAT	RW	RW	0	Software Reset For DAT line This bit is used in SD/eMMC mode and it resets only a part of the data circuit and the DMA circuit is also reset. The following registers and bits are cleared by this bit: - Buffer Data Port register - Buffer is cleared and initialized. - Present state register - Buffer Read Enable - Buffer Write Enable - Read Transfer Active - Write Transfer Active - DAT Line Active - Command Inhibit (DAT) - Block Gap Control register - Continue Request - Stop At Block Gap Request - Normal Interrupt status register - Buffer Read Ready - Buffer Write Ready - DMA Interrupt - Block Gap Event - Transfer Complete Values: - 0x0 (FALSE): Work - 0x1 (TRUE): Reset

25.3.2.20 SDHC_CORE_NORMAL_INT_STAT_R

Description: Normal Interrupt Status Register

Address: 0x40461030

Offset: 0x30

Retention: Retained

IsDeepSleep: No

Comment: This register reflects the status of the Normal Interrupt. This register is applicable for an SD/eMMC/UHS-II mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CARD_REMOVAL [7:7]	CARD_INSE RTION [6:6]	BUF_RD_READY [5:5]	BUF_WR_READY [4:4]	DMA_INTER RUPT [3:3]	BGAP_EVENT [2:2]	XFER_COMP LÊTE [1:1]	CMD_COMPL ÊTE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	ERR_INTER RUPT [15:15]	CQE_EVENT [14:14]	FX_EVENT [13:13]	None [12:9]				CARD_INTE RRUPT [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_COMPLETE	RW1C	RW1C	0	Command Complete In an SD/eMMC Mode, this bit is set when the end bit of a response except for Auto CMD12 and Auto CMD23. This interrupt is not generated when the Response Interrupt Disable in Transfer Mode Register is set to 1. Values: - 0x0 (FALSE): No command complete - 0x1 (TRUE): Command Complete
1	XFER_COMPLETE	RW1C	RW1C	0	Transfer Complete This bit is set when a read/write transfer and a command with status busy is completed. Values: - 0x0 (FALSE): Not complete - 0x1 (TRUE): Command execution is completed
2	BGAP_EVENT	RW1C	RW1C	0	Block Gap Event This bit is set when both read/write transaction is stopped at block gap due to a Stop at Block Gap Request. Values: - 0x0 (FALSE): No Block Gap Event - 0x1 (TRUE): Transaction stopped at block gap

Bits	Name	SW	HW	Default or Enum	Description
3	DMA_INTERRUPT	RW1C	RW1C	0	DMA Interrupt This bit is set if the Host Controller detects the SDMA Buffer Boundary during transfer. In case of ADMA, by setting the Int field in the descriptor table, the Host controller generates this interrupt. This interrupt is not generated after a Transfer Complete. Values: - 0x0 (FALSE): No DMA Interrupt - 0x1 (TRUE): DMA Interrupt is generated
4	BUF_WR_READY	RW1C	RW1C	0	Buffer Write Ready This bit is set if the Buffer Write Enable changes from 0 to 1. Values: - 0x0 (FALSE): Not ready to write buffer - 0x1 (TRUE): Ready to write buffer
5	BUF_RD_READY	RW1C	RW1C	0	Buffer Read Ready This bit is set if the Buffer Read Enable changes from 0 to 1. Values: - 0x0 (FALSE): Not ready to read buffer - 0x1 (TRUE): Ready to read buffer
6	CARD_INSERTION	RW1C	RW1C	0	Card Insertion This bit is set if the Card Inserted in the Present State register changes from 0 to 1. Values: - 0x0 (FALSE): Card state stable or Debouncing - 0x1 (TRUE): Card Inserted
7	CARD_REMOVAL	RW1C	RW1C	0	Card Removal This bit is set if the Card Inserted in the Present State register changes from 1 to 0. Values: - 0x0 (FALSE): Card state stable or Debouncing - 0x1 (TRUE): Card Removed
8	CARD_INTERRUPT	R	R	0	Card Interrupt This bit reflects the synchronized value of: - DAT[1] Interrupt Input for SD Mode Values: - 0x0 (FALSE): No Card Interrupt - 0x1 (TRUE): Generate Card Interrupt
13	FX_EVENT	R	R	0	FX Event This status is set when R[14] of response register is set to 1 and Response Type R1/R5 is set to 0 in Transfer Mode register. This interrupt is used with response check function. Values: - 0x0 (FALSE): No Event - 0x1 (TRUE): FX Event is detected

Bits	Name	SW	HW	Default or Enum	Description
14	CQE_EVENT	RW1C	RW1C	0	Command Queuing Event This status is set if Command Queuing/Crypto related event has occurred in eMMC/SD mode. Read CQHCI's CQIS/CRNQIS register for more details. In UHS-II Mode, this bit is irrelevant. Values: - 0x0 (FALSE): No Event - 0x1 (TRUE): Command Queuing Event is detected
15	ERR_INTERRUPT	R	R	0	Error Interrupt If any of the bits in the Error Interrupt Status register are set, then this bit is set. Values: - 0x0 (FALSE): No Error - 0x1 (TRUE): Error

25.3.2.21 SDHC_CORE_ERROR_INT_STAT_R

Description: Error Interrupt Status Register
Address: 0x40461032
Offset: 0x32
Retention: Retained
IsDeepSleep: No
Comment: This register enables an interrupt when the Error Interrupt Status Enable is enabled and at least one of the statuses is set to 1. Writing to 1 clears the bit and writing to 0 retains the bit unchanged. Signals defined in this register can be enabled by the Error Interrupt Status Enable register, but not by the Error Interrupt Signal Enable register. More than one status can be cleared with a single register write. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUR_LMT_ERR [7:7]	DATA_END_BIT_ERR [6:6]	DATA_CRC_ERR [5:5]	DATA_TOUT_ERR [4:4]	CMD_IDX_ERR [3:3]	CMD_END_BIT_ERR [2:2]	CMD_CRC_ERR [1:1]	CMD_TOUT_ERR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			BOOT_ACK_ERR [12:12]	RESP_ERR [11:11]	TUNING_ERR [10:10]	ADMA_ERR [9:9]	AUTO_CMD_ERR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_TOUT_ERR	RW1C	RW1C	0	Command Timeout Error In SD/eMMC Mode, this bit is set only if no response is returned within 64 SD clock cycles from the end bit of the command. If the Host Controller detects a CMD line conflict, along with Command CRC Error bit, this bit is set to 1, without waiting for 64 SD/eMMC card clock cycles. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Time out

Bits	Name	SW	HW	Default or Enum	Description
1	CMD_CRC_ERR	RW1C	RW1C	0	Command CRC Error Command CRC Error is generated in SD/eMMC mode for following two cases. - If a response is returned and the Command Timeout Error is set to 0 (indicating no timeout), this bit is set to 1 when detecting a CRC error in the command response. - The Host Controller detects a CMD line conflict by monitoring the CMD line when a command is issued. If the Host Controller drives the CMD line to 1 level, but detects 0 level on the CMD line at the next SD clock edge, then the Host Controller aborts the command (stop driving CMD line) and set this bit to 1. The Command Timeout Error is also set to 1 to distinguish a CMD line conflict. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): CRC error generated
2	CMD_END_BIT_ERR	RW1C	RW1C	0	Command End Bit Error This bit is set when detecting that the end bit of a command response is 0 in SD/eMMC mode. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): End Bit error generated
3	CMD_IDX_ERR	RW1C	RW1C	0	Command Index Error This bit is set if a Command Index error occurs in the command responds in SD/eMMC mode. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error
4	DATA_TOUT_ERR	RW1C	RW1C	0	Data Timeout Error This bit is set in SD/eMMC mode when detecting one of the following timeout conditions: - Busy timeout for R1b, R5b type - Busy timeout after Write CRC status - Write CRC Status timeout - Read Data timeout Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Time out
5	DATA_CRC_ERR	RW1C	RW1C	0	Data CRC Error This error occurs in SD/eMMC mode when detecting CRC error when transferring read data which uses the DAT line, when detecting the Write CRC status having a value of other than 010 or when write CRC status timeout. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error

Bits	Name	SW	HW	Default or Enum	Description
6	DATA_END_BIT_ERR	RW1C	RW1C	0	Data End Bit Error This error occurs in SD/eMMC mode either when detecting 0 at the end bit position of read data that uses the DAT line or at the end bit position of the CRC status. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error
7	CUR_LMT_ERR	RW1C	RW1C	0	Current Limit Error By setting the SD Bus Power bit in the Power Control register, the Host Controller is requested to supply power for the SD Bus. If the Host Controller supports the Current Limit function, it can be protected from an illegal card by stopping power supply to the card in which case this bit indicates a failure status. A reading of 1 for this bit means that the Host Controller is not supplying power to the SD card due to some failure. A reading of 0 for this bit means that the Host Controller is supplying power and no error has occurred. The Host Controller may require some sampling time to detect the current limit. DWC_mshc Host Controller does not support this function, this bit is always set to 0. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Power Fail
8	AUTO_CMD_ERR	RW1C	RW1C	0	Auto CMD Error This error status is used by Auto CMD12 and Auto CMD23 in SD/eMMC mode. This bit is set when detecting that any of the bits D00 to D05 in Auto CMD Error Status register has changed from 0 to 1. D07 is effective in case of Auto CMD12. Auto CMD Error Status register is valid while this bit is set to 1 and may be cleared by clearing of this bit. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error

Bits	Name	SW	HW	Default or Enum	Description
9	ADMA_ERR	RW1C	RW1C	0	ADMA Error This bit is set when the Host Controller detects error during ADMA-based data transfer. The error could be due to following reasons: - Error response received from System bus (Master I/F) - ADMA3,ADMA2 Descriptors invalid - CQE Task or Transfer descriptors invalid When the error occurs, the state of the ADMA is saved in the ADMA Error Status register. In eMMC CQE mode: The Host Controller generates this Interrupt when it detects an invalid descriptor data (Valid=0) at the ST_FDS state. ADMA Error State in the ADMA Error Status indicates that an error has occurred in ST_FDS state. The Host Driver may find that Valid bit is not set at the error descriptor. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error
10	TUNING_ERR	RW1C	RW1C	0	Reserved
11	RESP_ERR	RW1C	RW1C	0	Response Error Host Controller Version 4.00 supports response error check function to avoid overhead of response error check by Host Driver during DMA execution. If Response Error Check Enable is set to 1 in the Transfer Mode register, Host Controller Checks R1 or R5 response. If an error is detected in a response, this bit is set to 1. This is applicable in SD/eMMC mode. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error
12	BOOT_ACK_ERR	RW1C	RW1C	0	Boot Acknowledgement Error This bit is set when there is a timeout for boot acknowledgement or when detecting boot ack status having a value other than 010. This is applicable only when boot acknowledgement is expected in eMMC mode. In SD mode, this bit is irrelevant. Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error

25.3.2.22 SDHC_CORE_NORMAL_INT_STAT_EN_R

Description: Normal Interrupt Status Enable Register
Address: 0x40461034
Offset: 0x34
Retention: Retained
IsDeepSleep: No
Comment: This register enables the Interrupt Status for Normal Interrupt Status register (NORMAL_INT_STAT_R) when NORMAL_INT_STAT_R is set to 1. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CARD_REMOVAL_STAT_EN [7:7]	CARD_INSERTION_STAT_EN [6:6]	BUF_RD_READY_STAT_EN [5:5]	BUF_WR_READY_STAT_EN [4:4]	DMA_INTERRUPT_STAT_EN [3:3]	BGAP_EVENT_STAT_EN [2:2]	XFER_COMPLETE_STAT_EN [1:1]	CMD_COMPLETE_STAT_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	CQE_EVENT_STAT_EN [14:14]	FX_EVENT_STAT_EN [13:13]	RE_TUNE_EVENT_STAT_EN [12:12]	INT_C_STAT_T_EN [11:11]	INT_B_STAT_T_EN [10:10]	INT_A_STAT_T_EN [9:9]	CARD_INTERRUPT_STAT_EN [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_COMPLETE_STAT_EN	RW	RW	0	Command Complete Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
1	XFER_COMPLETE_STAT_EN	RW	RW	0	Transfer Complete Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
2	BGAP_EVENT_STAT_EN	RW	RW	0	Block Gap Event Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
3	DMA_INTERRUPT_STAT_EN	RW	RW	0	DMA Interrupt Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
4	BUF_WR_READY_STAT_EN	RW	RW	0	Buffer Write Ready Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
5	BUF_RD_READY_STAT_EN	RW	RW	0	Buffer Read Ready Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled

Bits	Name	SW	HW	Default or Enum	Description
6	CARD_INSERTION_STAT_EN	RW	RW	0	Card Insertion Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
7	CARD_REMOVAL_STAT_EN	RW	RW	0	Card Removal Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
8	CARD_INTERRUPT_STAT_EN	RW	RW	0	Card Interrupt Status Enable If this bit is set to 0, the Host Controller clears the interrupt request to the System. The Card Interrupt detection is stopped when this bit is cleared and restarted when this bit is set to 1. The Host Driver may clear the Card Interrupt Status Enable before servicing the Card Interrupt and may set this bit again after all interrupt requests from the card are cleared to prevent inadvertent interrupts. Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
9	INT_A_STAT_EN	RW	RW	0	Reserved: set to 0
10	INT_B_STAT_EN	RW	RW	0	Reserved: set to 0
11	INT_C_STAT_EN	RW	RW	0	Reserved: set to 0
12	RE_TUNE_EVENT_STAT_EN	RW	RW	0	Reserved: set to 0
13	FX_EVENT_STAT_EN	RW	RW	0	FX Event Status Enable This bit is added from Version 4.10. Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
14	CQE_EVENT_STAT_EN	RW	RW	0	CQE Event Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled

25.3.2.23 SDHC_CORE_ERROR_INT_STAT_EN_R

Description: Error Interrupt Status Enable Register
Address: 0x40461036
Offset: 0x36
Retention: Retained
IsDeepSleep: No
Comment: This register sets the Interrupt Status for Error Interrupt Status register (ERROR_INT_STAT_R), when ERROR_INT_STAT_EN_R is set to 1. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUR_LMT_ERR_STAT_EN [7:7]	DATA_END_BIT_ERR_STAT_EN [6:6]	DATA_CRC_ERR_STAT_EN [5:5]	DATA_TOUT_ERR_STAT_EN [4:4]	CMD_IDX_ERR_STAT_EN [3:3]	CMD_END_BIT_ERR_STAT_EN [2:2]	CMD_CRC_ERR_STAT_EN [1:1]	CMD_TOUT_ERR_STAT_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	VENDOR_ERR_STAT_EN3 [15:15]	VENDOR_ERR_STAT_EN2 [14:14]	VENDOR_ERR_STAT_EN1 [13:13]	BOOT_ACK_ERR_STAT_EN [12:12]	RESP_ERR_STAT_EN [11:11]	TUNING_ERR_STAT_EN [10:10]	ADMA_ERR_STAT_EN [9:9]	AUTO_CMD_ERR_STAT_EN [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_TOUT_ERR_STAT_EN	RW	RW	0	Command Timeout Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
1	CMD_CRC_ERR_STAT_EN	RW	RW	0	Command CRC Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
2	CMD_END_BIT_ERR_STAT_EN	RW	RW	0	Command End Bit Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
3	CMD_IDX_ERR_STAT_EN	RW	RW	0	Command Index Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled

Bits	Name	SW	HW	Default or Enum	Description
4	DATA_TOUT_ERR_STAT_EN	RW	RW	0	Data Timeout Error Status Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
5	DATA_CRC_ERR_STAT_EN	RW	RW	0	Data CRC Error Status Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
6	DATA_END_BIT_ERR_STAT_EN	RW	RW	0	Data End Bit Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
7	CUR_LMT_ERR_STAT_EN	RW	RW	0	Current Limit Error Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
8	AUTO_CMD_ERR_STAT_EN	RW	RW	0	Auto CMD Error Status Enable (SD/eMMC Mode only). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
9	ADMA_ERR_STAT_EN	RW	RW	0	ADMA Error Status Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
10	TUNING_ERR_STAT_EN	RW	RW	0	Tuning Error Status Enable (UHS-I Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
11	RESP_ERR_STAT_EN	RW	RW	0	Response Error Status Enable (SD Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
12	BOOT_ACK_ERR_STAT_EN	RW	RW	0	Boot Acknowledgment Error (eMMC Mode only) Setting this bit to 1 enables setting of Boot Acknowledgment Error in Error Interrupt Status register (ERROR_INT_STAT_R). Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
13	VENDOR_ERR_STAT_EN1	RW	RW	0	Reserved: set to 0
14	VENDOR_ERR_STAT_EN2	RW	RW	0	Reserved: set to 0
15	VENDOR_ERR_STAT_EN3	RW	RW	0	Reserved: set to 0

25.3.2.24 SDHC_CORE_NORMAL_INT_SIGNAL_EN_R

Description: Normal Interrupt Signal Enable Register

Address: 0x40461038

Offset: 0x38

Retention: Retained

IsDeepSleep: No

Comment: This register is used to select the interrupt status that is indicated to the Host System as the interrupt. All these status bits share the same 1-bit interrupt line. Setting any of these bits to 1, enables interrupt generation. This register is applicable for an SD/eMMC/UHS-II mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CARD_REMOVAL_SIGNAL_EN [7:7]	CARD_INSERTION_SIGNAL_EN [6:6]	BUF_RD_READY_SIGNAL_EN [5:5]	BUF_WR_READY_SIGNAL_EN [4:4]	DMA_INTERRUPT_SIGNAL_EN [3:3]	BGAP_EVENT_SIGNAL_EN [2:2]	XFER_COMPLETE_SIGNAL_EN [1:1]	CMD_COMPLETE_SIGNAL_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	CQE_EVENT_SIGNAL_EN [14:14]	FX_EVENT_SIGNAL_EN [13:13]	RE_TUNE_EVENT_SIGNAL_EN [12:12]	INT_C_SIGNAL_EN [11:11]	INT_B_SIGNAL_EN [10:10]	INT_A_SIGNAL_EN [9:9]	CARD_INTERRUPT_SIGNAL_EN [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_COMPLETE_SIGNAL_EN	RW	RW	0	Command Complete Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
1	XFER_COMPLETE_SIGNAL_EN	RW	RW	0	Transfer Complete Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
2	BGAP_EVENT_SIGNAL_EN	RW	RW	0	Block Gap Event Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
3	DMA_INTERRUPT_SIGNAL_EN	RW	RW	0	DMA Interrupt Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
4	BUF_WR_READY_SIGNAL_EN	RW	RW	0	Buffer Write Ready Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
5	BUF_RD_READY_SIGNAL_EN	RW	RW	0	Buffer Read Ready Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled

Bits	Name	SW	HW	Default or Enum	Description
6	CARD_INSERTION_SIGNAL_EN	RW	RW	0	Card Insertion Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
7	CARD_REMOVAL_SIGNAL_EN	RW	RW	0	Card Removal Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
8	CARD_INTERRUPT_SIGNAL_EN	RW	RW	0	Card Interrupt Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
9	INT_A_SIGNAL_EN	RW	RW	0	Reserved: set to 0
10	INT_B_SIGNAL_EN	RW	RW	0	Reserved: set to 0
11	INT_C_SIGNAL_EN	RW	RW	0	Reserved: set to 0
12	RE_TUNE_EVENT_SIGNAL_EN	RW	RW	0	Reserved: set to 0
13	FX_EVENT_SIGNAL_EN	RW	RW	0	FX Event Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
14	CQE_EVENT_SIGNAL_EN	RW	RW	0	Command Queuing Engine Event Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled

25.3.2.25 SDHC_CORE_ERROR_INT_SIGNAL_EN_R

Description: Error Interrupt Signal Enable Register
Address: 0x4046103A
Offset: 0x3A
Retention: Retained
IsDeepSleep: No
Comment: This register is used to select the interrupt status that is notified to the Host System as an interrupt. All these status bits share the same 1-bit interrupt line. Setting any of these bits to 1 enables interrupt generation. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CUR_LMT_ERR_SIGNAL_EN [7:7]	DATA_END_BIT_ERR_SIGNAL_EN [6:6]	DATA_CRC_ERR_SIGNAL_EN [5:5]	DATA_TOUT_ERR_SIGNAL_EN [4:4]	CMD_IDX_ERR_SIGNAL_EN [3:3]	CMD_END_BIT_ERR_SIGNAL_EN [2:2]	CMD_CRC_ERR_SIGNAL_EN [1:1]	CMD_TOUT_ERR_SIGNAL_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	VENDOR_ERR_SIGNAL_EN3 [15:15]	VENDOR_ERR_SIGNAL_EN2 [14:14]	VENDOR_ERR_SIGNAL_EN1 [13:13]	BOOT_ACK_ERR_SIGNAL_EN [12:12]	RESP_ERR_SIGNAL_EN [11:11]	TUNING_ERR_SIGNAL_EN [10:10]	ADMA_ERR_SIGNAL_EN [9:9]	AUTO_CMD_ERR_SIGNAL_EN [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_TOUT_ERR_SIGNAL_EN	RW	RW	0	Command Timeout Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
1	CMD_CRC_ERR_SIGNAL_EN	RW	RW	0	Command CRC Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
2	CMD_END_BIT_ERR_SIGNAL_EN	RW	RW	0	Command End Bit Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
3	CMD_IDX_ERR_SIGNAL_EN	RW	RW	0	Command Index Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): No error - 0x1 (TRUE): Error

Bits	Name	SW	HW	Default or Enum	Description
4	DATA_TOUT_ERR_SIGNAL_EN	RW	RW	0	Data Timeout Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
5	DATA_CRC_ERR_SIGNAL_EN	RW	RW	0	Data CRC Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
6	DATA_END_BIT_ERR_SIGNAL_EN	RW	RW	0	Data End Bit Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
7	CUR_LMT_ERR_SIGNAL_EN	RW	RW	0	Current Limit Error Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
8	AUTO_CMD_ERR_SIGNAL_EN	RW	RW	0	Auto CMD Error Signal Enable (SD/eMMC Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
9	ADMA_ERR_SIGNAL_EN	RW	RW	0	ADMA Error Signal Enable Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
10	TUNING_ERR_SIGNAL_EN	RW	RW	0	Reserved: set to 0
11	RESP_ERR_SIGNAL_EN	RW	RW	0	Response Error Signal Enable (SD Mode only) Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
12	BOOT_ACK_ERR_SIGNAL_EN	RW	RW	0	Boot Acknowledgment Error (eMMC Mode only). Setting this bit to 1 enables generating interrupt signal when Boot Acknowledgment Error in Error Interrupt Status register is set. Values: - 0x0 (FALSE): Masked - 0x1 (TRUE): Enabled
13	VENDOR_ERR_SIGNAL_EN1	RW	RW	0	Reserved: set to 0
14	VENDOR_ERR_SIGNAL_EN2	RW	RW	0	Reserved: set to 0
15	VENDOR_ERR_SIGNAL_EN3	RW	RW	0	Reserved: set to 0

25.3.2.26 SDHC_CORE_AUTO_CMD_STAT_R

Description: Auto CMD Status Register

Address: 0x4046103C

Offset: 0x3C

Retention: Retained

IsDeepSleep: No

Comment: This register is used to indicate the CMD12 response error of Auto CMD12, and the CMD23 response error of Auto CMD23. The Host driver can determine the kind of Auto CMD12/CMD23 errors that can occur in this register. Auto CMD23 errors are indicated in bit 04-01.

This register is valid only when Auto CMD Error is set. This register is applicable for an SD/eMMC mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CMD_NOT_ISSUED_AUTO_CMD12 [7:7]	None [6:6]	AUTO_CMD_RESP_ERR [5:5]	AUTO_CMD_IDX_ERR [4:4]	AUTO_CMD_EBIT_ERR [3:3]	AUTO_CMD_CRC_ERR [2:2]	AUTO_CMD_TOUT_ERR [1:1]	AUTO_CMD12_NOT_EXEC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	AUTO_CMD12_NOT_EXEC	R	R	0	Auto CMD12 Not Executed If multiple memory block data transfer is not started due to a command error, this bit is not set because it is not necessary to issue an Auto CMD12. Setting this bit to 1 means that the Host Controller cannot issue Auto CMD12 to stop multiple memory block data transfer, due to some error. If this bit is set to 1, error status bits (D04-D01) is meaningless. This bit is set to 0 when Auto CMD Error is generated by Auto CMD23. Values: - 0x1 (TRUE): Not Executed - 0x0 (FALSE): Executed

Bits	Name	SW	HW	Default or Enum	Description
1	AUTO_CMD_TOUT_ERR	R	R	0	Auto CMD Timeout Error This bit is set if no response is returned with 64 SDCLK cycles from the end bit of the command. If this bit is set to 1, error status bits (D04-D01) are meaningless. Values: - 0x1 (TRUE): Time out - 0x0 (FALSE): No Error
2	AUTO_CMD_CRC_ERR	R	R	0	Auto CMD CRC Error This bit is set when detecting a CRC error in the command response. Values: - 0x1 (TRUE): CRC Error Generated - 0x0 (FALSE): No Error
3	AUTO_CMD_EBIT_ERR	R	R	0	Auto CMD End Bit Error This bit is set when detecting that the end bit of command response is 0. Values: - 0x1 (TRUE): End Bit Error Generated - 0x0 (FALSE): No Error
4	AUTO_CMD_IDX_ERR	R	R	0	Auto CMD Index Error This bit is set if the command index error occurs in response to a command. Values: - 0x1 (TRUE): Error - 0x0 (FALSE): No Error
5	AUTO_CMD_RESP_ERR	R	R	0	Auto CMD Response Error This bit is set when Response Error Check Enable in the Transfer Mode register is set to 1 and an error is detected in R1 response of either Auto CMD12 or CMD13. This status is ignored if any bit between D00 to D04 is set to 1. Values: - 0x1 (TRUE): Error - 0x0 (FALSE): No Error
7	CMD_NOT_ISSUED_AUTO_CMD12	R	R	0	Command Not Issued By Auto CMD12 Error If this bit is set to 1, CMD_wo_DAT is not executed due to an Auto CMD12 Error (D04-D01) in this register. This bit is set to 0 when Auto CMD Error is generated by Auto CMD23. Values: - 0x1 (TRUE): Not Issued - 0x0 (FALSE): No Error

25.3.2.27 SDHC_CORE_HOST_CTRL2_R

Description: Host Control 2 Register
Address: 0x4046103E
Offset: 0x3E
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control how the Host Controller operates. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SAMPLE_CLK_SEL [7:7]	EXEC_TUNING [6:6]	DRV_STRENGTH_SEL [5:4]		SIGNALING_EN [3:3]	UHS_MODE_SEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	PRESET_VAL_ENABLE [15:15]	ASYNC_INT_ENABLE [14:14]	ADDRESSING [13:13]	HOST_VER4_ENABLE [12:12]	CMD23_ENABLE [11:11]	ADMA2_LEN_MODE [10:10]	None [9:9]	UHS2_IF_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	UHS_MODE_SEL	RW	RW	0	UHS Mode/eMMC Speed Mode Select These bits are used to select UHS mode in the SD mode of operation. In eMMC mode, these bits are used to select eMMC Speed mode. UHS-I Mode: - 0x0: SDR12 - 0x1: SDR25 - 0x2: SDR50 - 0x3: Reserved - 0x4: DDR50 - 0x5: Reserved - 0x6: Reserved - 0x7: Reserved eMMC Speed Mode (eMMC mode only): - 0x0: Legacy - 0x1: High Speed SDR - 0x2: Reserved - 0x3: Reserved - 0x4: High Speed DDR - 0x5: Reserved - 0x6: Reserved - 0x7: Reserved

Bits	Name	SW	HW	Default or Enum	Description
3	SIGNALING_EN	RW	RW	0	1.8V Signaling Enable This bit controls voltage regulator for I/O cell in SD UHS-I mode. Setting this bit from 0 to 1 starts changing the signal voltage from 3.3V to 1.8V. Host Controller clears this bit if switching to 1.8V signaling fails per protocol. The value is reflected on the io_volt_sel output which can then be used to change an external regulator to supply 1.8V instead of 3.3V on the VDDIO pin associated with the CLK/CMD/DAT signals. Note: This bit must be set for all UHS-I speed modes (SDR12/SDR25/SDR50/DDR50). Values: - 0x0 (V_3_3): 3.3V Signalling - 0x1 (V_1_8): 1.8V Signalling
4:5	DRV_STRENGTH_SEL	RW	RW	0	Driver Strength Select These bits are used to select the Host Controller output driver in 1.8V signaling UHS-I/eMMC speed modes. The value is reflected on the io_drive_strength[1:0] output. - 0x0 (TYPEB): Driver TYPEB is selected - 0x1 (TYPEA): Driver TYPEA is selected - 0x2 (TYPEEC): Driver TYPEEC is selected - 0x3 (TYPED): Driver TYPED is selected
6	EXEC_TUNING	RW	RW	0	Reserved: set to 0
7	SAMPLE_CLK_SEL	RW	RW	0	Reserved: set to 0
8	UHS2_IF_ENABLE	RW	RW	0	Reserved: set to 0
10	ADMA2_LEN_MODE	RW	RW	0	ADMA2 Length Mode This bit selects ADMA2 Length mode to be either 16-bit or 26-bit. Values: - 0x0 (FALSE): 16-bit Data Length Mode - 0x1 (TRUE): 26-bit Data Length Mode
11	CMD23_ENABLE	RW	RW	0	CMD23 Enable If the card supports CMD23, this bit is set to 1. This bit is used to select Auto CMD23 or Auto CMD12 for ADMA3 data transfer. Values: - 0x0 (FALSE): Auto CMD23 is disabled - 0x1 (TRUE): Auto CMD23 is enabled

Bits	Name	SW	HW	Default or Enum	Description
12	HOST_VER4_ENABLE	RW	RW	0	Host Version 4 Enable This bit selects either Version 3.00 compatible mode or Version 4 mode. Functions of following fields are modified for Host Version 4 mode: - SDMA Address: SDMA uses ADMA System Address (05Fh-058h) instead of SDMA System Address register (003h-000h) - ADMA2/ADMA3 selection: ADMA3 is selected by DMA select in Host Control 1 register - 32-bit Block Count: SDMA System Address register (003h-000h) is modified to 32-bit Block Count register Note: It is recommended not to program ADMA3 Integrated Descriptor Address registers and Command Queuing registers (if applicable) while operating in Host version less than 4 mode (Host Version 4 Enable = 0). Values: - 0x0 (FALSE): Version 3.00 compatible mode - 0x1 (TRUE): Version 4 mode
13	ADDRESSING	RW	RW	0	Reserved: set to 0
14	ASYNC_INT_ENABLE	RW	RW	0	Asynchronous Interrupt Enable This bit can be set if a card supports asynchronous interrupts and Asynchronous Interrupt Support is set to 1 in the Capabilities register. Values: - 0x0 (FALSE): Disabled - 0x1 (TRUE): Enabled
15	PRESET_VAL_ENABLE	RW	RW	0	Reserved: set to 0

25.3.2.28 SDHC_CORE_CAPABILITIES1_R

Description: Capabilities 1 Register - 0 to 31
Address: 0x40461040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: This register provides the Host Driver with information specific to the Host Controller implementation. The host controller may implement these values as fixed or loaded from the flash memory during power on initialization. Capabilities register is segregated into two 32-bit registers: CAPABILITIES1_R and CAPABILITIES2_R. The CAPABILITIES1_R register is the lower part of Capabilities register.
Default: 0x276C6481

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TOUT_CLK_UNIT [7:7]	None [6:6]	TOUT_CLK_FREQ [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	BASE_CLK_FREQ [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	SUS_RES_SUPPORT [23:23]	SDMA_SUPPORT [22:22]	HIGH_SPEED_SUPPORT [21:21]	None [20:20]	ADMA2_SUPPORT [19:19]	EMBEDDED_8_BIT [18:18]	MAX_BLK_LEN [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	SLOT_TYPE_R [31:30]		ASYNC_INT_SUPPORT [29:29]	SYS_ADDR_64_V3 [28:28]	SYS_ADDR_64_V4 [27:27]	VOLT_18 [26:26]	VOLT_30 [25:25]	VOLT_33 [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	TOUT_CLK_FREQ	R	R	1	Timeout Clock Frequency This bit shows the base clock frequency used to detect Data Timeout Error. The Timeout Clock unit defines the unit of timeout clock frequency. It can be KHz or MHz. - 0x00 - Get information through another method - 0x01 - 1KHz / 1MHz - 0x02 - 2KHz / 2MHz - 0x03 - 3KHz / 3MHz - - 0x3F - 63KHz / 63MHz
7	TOUT_CLK_UNIT	R	R	1	Timeout Clock Unit This bit shows the unit of base clock frequency used to detect Data Timeout Error. Values: - 0x0 (KHz): KHz - 0x1 (MHz): MHz

Bits	Name	SW	HW	Default or Enum	Description
8:15	BASE_CLK_FREQ	R	R	100	Base Clock Frequency for SD clock These bits indicate the base (maximum) clock frequency for the SD Clock. The definition of these bits depend on the Host Controller Version. - 6-Bit Base Clock Frequency: This mode is supported by the Host Controller version 1.00 and 2.00. The upper 2 bits are not effective and are always 0. The unit values are 1 MHz. The supported clock range is 10 MHz to 63 MHz. - 0x00 - Get information through another method - 0x01 - 1 MHz - 0x02 - 2 MHz - - 0x3F - 63 MHz - 0x40-0xFF - Not Supported - 8-Bit Base Clock Frequency: This mode is supported by the Host Controller version 3.00. The unit values are 1 MHz. The supported clock range is 10 MHz to 255 MHz. - 0x00 - Get information through another method - 0x01 - 1 MHz - 0x02 - 2 MHz - - 0xFF - 255 MHz If the frequency is 16.5 MHz, the larger value is set to 0001001b (17 MHz) because the Host Driver uses this value to calculate the clock divider value and it does not exceed the upper limit of the SD Clock frequency. If these bits are all 0, the Host system has to get information using a different method.
16:17	MAX_BLK_LEN	R	R	MAX_BLK_SIZE	Maximum Block Length This bit indicates the maximum block size that the Host driver can read and write to the buffer in the Host Controller. The buffer transfers this block size without wait cycles. The transfer block length is always 512 bytes for the SD Memory irrespective of this bit. Value is fixed to (including the default value): 0x0: when MAX_BLK_SIZE=0 indicating 512 Bytes 0x1: when MAX_BLK_SIZE=1 indicating 1024 Bytes 0x2: Reserved 0x3: Reserved
18	EMBEDDED_8_BIT	R	R	1	8-bit Support for Embedded Device This bit indicates whether the Host Controller is capable of using an 8-bit bus width mode. This bit is not effective when the Slot Type is set to 10b. Values: - 0x0 (FALSE): 8-bit Bus Width not Supported - 0x1 (TRUE): 8-bit Bus Width Supported

Bits	Name	SW	HW	Default or Enum	Description
19	ADMA2_SUPPORT	R	R	1	ADMA2 Support This bit indicates whether the Host Controller is capable of using ADMA2. Values: - 0x0 (FALSE): ADMA2 not Supported - 0x1 (TRUE): ADMA2 Supported
21	HIGH_SPEED_SUPPORT	R	R	1	High Speed Support This bit indicates whether the Host Controller and the Host System supports High Speed mode and they can supply the SD Clock frequency from 25 MHz to 50 MHz. Values: - 0x0 (FALSE): High Speed not Supported - 0x1 (TRUE): High Speed Supported
22	SDMA_SUPPORT	R	R	1	SDMA Support This bit indicates whether the Host Controller is capable of using SDMA to transfer data between the system memory and the Host Controller directly. Values: - 0x0 (FALSE): SDMA not Supported - 0x1 (TRUE): SDMA Supported
23	SUS_RES_SUPPORT	R	R	0	Suspend/Resume Support This bit indicates whether the Host Controller supports Suspend/Resume functionality. If this bit is 0, the Host Driver does not issue either Suspend or Resume commands because the Suspend and Resume mechanism is not supported. Values: - 0x0 (FALSE): Not Supported - 0x1 (TRUE): Supported
24	VOLT_33	R	R	1	Voltage Support 3.3V Values: - 0x0 (FALSE): 3.3V Not Supported - 0x1 (TRUE): 3.3V Supported
25	VOLT_30	R	R	1	Voltage Support 3.0V Values: - 0x0 (FALSE): 3.0V Not Supported - 0x1 (TRUE): 3.0V Supported
26	VOLT_18	R	R	1	Voltage Support 1.8V Values: - 0x0 (FALSE): 1.8V Not Supported - 0x1 (TRUE): 1.8V Supported

Bits	Name	SW	HW	Default or Enum	Description
27	SYS_ADDR_64_V4	R	R	0	64-bit System Address Support for V4 This bit sets the Host Controller to support 64-bit System Addressing of V4 mode. When this bit is set to 1, full or part of 64-bit address must be used to decode the Host Controller Registers so that Host Controller Registers can be placed above system memory area. 64-bit address decode of Host Controller registers is effective regardless of setting to 64-bit Addressing in Host Control 2. If this bit is set to 1, 64-bit DMA Addressing for version 4 is enabled by setting Host Version 4 Enable (HOST_VER4_ENABLE = 1) and by setting 64-bit Addressing (ADDRESSING = 1) in the Host Control 2 register. SDMA can be used and ADMA2 uses 128-bit Descriptor. Values: - 0x0 (FALSE): 64-bit System Address for V4 is Not Supported - 0x1 (TRUE): 64-bit System Address for V4 is Supported
28	SYS_ADDR_64_V3	R	R	0	64-bit System Address Support for V3 This bit sets the Host controller to support 64-bit System Addressing of V3 mode. SDMA cannot be used in 64-bit Addressing in Version 3 Mode. If this bit is set to 1, 64-bit ADMA2 with using 96-bit Descriptor can be enabled by setting Host Version 4 Enable (HOST_VER4_ENABLE = 0) and DMA select (DMA_SEL = 11b). Values: - 0x0 (FALSE): 64-bit System Address for V3 is Not Supported - 0x1 (TRUE): 64-bit System Address for V3 is Supported
29	ASYNC_INT_SUPPORT	R	R	1	Asynchronous Interrupt Support (SD Mode only) Values: - 0x0 (FALSE): Asynchronous Interrupt Not Supported - 0x1 (TRUE): Asynchronous Interrupt Supported
30:31	SLOT_TYPE_R	R	R	0	Slot Type These bits indicate usage of a slot by a specific Host System. Values: - 0x0 (REMOVABLE_SLOT): Removable Card Slot - 0x1 (EMBEDDED_SLOT): Embedded Slot for one Device - 0x2 (SHARED_SLOT): Shared Bus Slot (SD mode) - 0x3 (UHS2_EMBEDDED_SLOT): UHS-II Multiple Embedded Devices

25.3.2.29 SDHC_CORE_CAPABILITIES2_R

Description: Capabilities Register - 32 to 63
Address: 0x40461044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: register provides the Host Driver with information specific to the Host Controller implementation. The host controller may implement these values as fixed or as loaded from flash memory during power on initialization. Capabilities register is segregated into two 32-bit registers, namely CAPABILITIES1_R and CAPABILITIES2_R. The CAPABILITIES2_R register is upper part of Capabilities register.
Default: 0x8000077

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	DRV _TYPED [6:6]	DRV _TYPEPEC [5:5]	DRV _TYPEA [4:4]	UHS2 _SUPPORT [3:3]	DDR50 _SUPPORT [2:2]	SDR104 _SUPPORT [1:1]	SDR50 _SUPPORT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	RE_TUNING_MODES [15:14]		USE _TUNING _SDR50 [13:13]	None [12:12]	RETUNE_CNT [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	CLK_MUL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:29]			VDD2_18V _SUPPORT [28:28]	ADMA3 _SUPPORT [27:27]	None [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SDR50_SUPPORT	R	R	1	SDR50 Support (UHS-I only) This bit indicates that SDR50 is supported. The bit 13 (USE_TUNING_SDR50) indicates whether SDR50 requires tuning or not. Values: - 0x0 (FALSE): SDR50 is not supported - 0x1 (TRUE): SDR50 is supported
1	SDR104_SUPPORT	R	R	1	SDR104 Support (UHS-I only) This bit mentions that SDR104 requires tuning. Values: - 0x0 (FALSE): SDR104 is not supported - 0x1 (TRUE): SDR104 is supported (NOT ACTUALLY SUPPORTED)
2	DDR50_SUPPORT	R	R	1	DDR50 Support (UHS-I only) Values: - 0x0 (FALSE): DDR50 is not supported - 0x1 (TRUE): DDR50 is supported

Bits	Name	SW	HW	Default or Enum	Description
3	UHS2_SUPPORT	R	R	0	UHS-II Support (UHS-II only) This bit indicates whether Host Controller supports UHS-II. Values: - 0x0 (FALSE): UHS-II is not supported - 0x1 (TRUE): UHS-II is supported
4	DRV_TYPEA	R	R	1	Driver Type A Support (UHS-I only) This bit indicates support of Driver Type A for 1.8 Signaling. Values: - 0x0 (FALSE): Driver Type A is not supported - 0x1 (TRUE): Driver Type A is supported
5	DRV_TYPEC	R	R	1	Driver Type C Support (UHS-I only) This bit indicates support of Driver Type C for 1.8 Signaling. Values: - 0x0 (FALSE): Driver Type C is not supported - 0x1 (TRUE): Driver Type C is supported
6	DRV_TYPED	R	R	1	Driver Type D Support (UHS-I only) This bit indicates support of Driver Type D for 1.8 Signaling. Values: - 0x0 (FALSE): Driver Type D is not supported - 0x1 (TRUE): Driver Type D is supported
8:11	RETUNE_CNT	R	R	0	Timer Count for Re-Tuning (UHS-I only) - 0x0: Re-Tuning Timer disabled - 0x1: 1 seconds - 0x2: 2 seconds - 0x3: 4 seconds - - 0xB: 1024 seconds - 0xC: Reserved - 0xD: Reserved - 0xE: Reserved - 0xF: Get information from other source
13	USE_TUNING_SDR50	R	R	0	Use Tuning for SDR50 (UHS-I only) Values: - 0x0 (ZERO): SDR50 does not require tuning - 0x1 (ONE): SDR50 requires tuning
14:15	RE_TUNING_MODES	R	R	0	Re-Tuning Modes (UHS-I only) These bits select the re-tuning method and limit the maximum data length. Values: - 0x0 (MODE1): Timer - 0x1 (MODE2): Timer and Re-Tuning Request (Not supported) - 0x2 (MODE3): Auto Re-Tuning (for transfer) - 0x3 (RSVD_MODE): Reserved
16:23	CLK_MUL	R	R	0	Clock Multiplier These bits indicate the clock multiplier of the programmable clock generator. Setting these bits to 0 means that the Host Controller does not support a programmable clock generator. - 0x0: Clock Multiplier is not Supported - 0x1: Clock Multiplier M = 2 - 0x2: Clock Multiplier M = 3 - - 0xFF: Clock Multiplier M = 256

Bits	Name	SW	HW	Default or Enum	Description
27	ADMA3_SUPPORT	R	R	1	ADMA3 Support This bit indicates whether the Host Controller is capable of using ADMA3. Values: - 0x0 (FALSE): ADMA3 not Supported - 0x1 (TRUE): ADMA3 Supported
28	VDD2_18V_SUPPORT	R	R	0	1.8V VDD2 Support This bit indicates support of VDD2 for the Host System. Values: - 0x0 (FALSE): 1.8V VDD2 is not Supported - 0x1 (TRUE): 1.8V VDD2 is Supported

25.3.2.30 SDHC_CORE_CURR_CAPABILITIES1_R

Description: Current Capabilities Register - 0 to 31
Address: 0x40461048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: This register indicate the maximum current capability for each voltage, for VDD1. The value is meaningful if the Voltage Support is set in the Capabilities register. If this information is supplied by the Host System through another method, all the Maximum Current Capabilities registers are set to 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MAX_CUR_33V [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	MAX_CUR_30V [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	MAX_CUR_18V [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	MAX_CUR_33V	R	R	0	Maximum Current for 3.3V This bit specifies the Maximum Current for 3.3V VDD1 power supply for the card. - 0: Get information through another method - 1: 4mA - 2: 8mA - 3: 13mA - - 255: 1020mA
8:15	MAX_CUR_30V	R	R	0	Maximum Current for 3.0V This bit specifies the Maximum Current for 3.0V VDD1 power supply for the card. - 0: Get information through another method - 1: 4mA - 2: 8mA - 3: 13mA - - 255: 1020mA
16:23	MAX_CUR_18V	R	R	0	Maximum Current for 1.8V This bit specifies the Maximum Current for 1.8V VDD1 power supply for the card. - 0: Get information through another method - 1: 4mA - 2: 8mA - 3: 13mA - - 255: 1020mA

25.3.2.31 SDHC_CORE_CURR_CAPABILITIES2_R

Description: Maximum Current Capabilities Register - 32 to 63
Address: 0x4046104C
Offset: 0x4C
Retention: Retained
IsDeepSleep: No
Comment: This register indicates the maximum current capability for each voltage (for VDD2). The value is meaningful if Voltage Support is set in the Capabilities register. If this information is supplied by the Host System through another method, all the Maximum Current Capabilities registers are set to 0.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MAX_CUR_VDD2_18V [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	MAX_CUR_VDD2_18V	R	R	0	Maximum Current for 1.8V VDD2 This bit specifies the Maximum Current for 1.8V VDD2 power supply for the UHS-II card. - 0: Get information through another method - 1: 4mA - 2: 8mA - 3: 13mA - - 255: 1020mA

25.3.2.32 SDHC_CORE_FORCE_AUTO_CMD_STAT_R

Description: Force Event Register for Auto CMD Error Status register
Address: 0x40461050
Offset: 0x50
Retention: Retained
IsDeepSleep: No
Comment: The register is not a physically implemented but is an address at which the Auto CMD Error Status register can be written. This register is applicable for an SD/eMMC mode.
- 1 : Sets each bit of the Auto CMD Error Status register
- 0 : No effect
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FORCE_AUTO_CMD_NOT_ISSUED_AUTO_CMD12 [7:7]	None [6:6]	FORCE_AUTO_CMD_RESP_ERR [5:5]	FORCE_AUTO_CMD_IDX_ERR [4:4]	FORCE_AUTO_CMD_EBIT_ERR [3:3]	FORCE_AUTO_CMD_CRC_ERR [2:2]	FORCE_AUTO_CMD_TOUT_ERR [1:1]	FORCE_AUTO_CMD12_NOT_EXEC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FORCE_AUTO_CMD12_NOT_EXEC	W	W	0	Force Event for Auto CMD12 Not Executed Values: - 0x1 (TRUE): Auto CMD12 Not Executed Status is set - 0x0 (FALSE): Not Affected
1	FORCE_AUTO_CMD_TOUT_ERR	W	W	0	Force Event for Auto CMD Timeout Error Values: - 0x1 (TRUE): Auto CMD Timeout Error Status is set - 0x0 (FALSE): Not Affected
2	FORCE_AUTO_CMD_CRC_ERR	W	W	0	Force Event for Auto CMD CRC Error Values: - 0x1 (TRUE): Auto CMD CRC Error Status is set - 0x0 (FALSE): Not Affected
3	FORCE_AUTO_CMD_EBIT_ERR	W	W	0	Force Event for Auto CMD End Bit Error Values: - 0x1 (TRUE): Auto CMD End Bit Error Status is set - 0x0 (FALSE): Not Affected
4	FORCE_AUTO_CMD_IDX_ERR	W	W	0	Force Event for Auto CMD Index Error Values: - 0x1 (TRUE): Auto CMD Index Error Status is set - 0x0 (FALSE): Not Affected
5	FORCE_AUTO_CMD_RESP_ERR	W	W	0	Force Event for Auto CMD Response Error Values: - 0x1 (TRUE): Auto CMD Response Error Status is set - 0x0 (FALSE): Not Affected

Bits	Name	SW	HW	Default or Enum	Description
7	FORCE_CMD_NOT_ISSUED_AUTO_CMD12	W	W	0	Force Event for Command Not Issued By Auto CMD12 Error Values: - 0x1 (TRUE): Command Not Issued By Auto CMD12 Error Status is set - 0x0 (FALSE): Not Affected

25.3.2.33 SDHC_CORE_FORCE_ERROR_INT_STAT_R

Description: Force Event Register for Error Interrupt Status

Address: 0x40461052

Offset: 0x52

Retention: Retained

IsDeepSleep: No

Comment: This register is not physically implemented but is an address at which the Error Interrupt Status register can be written. The effect of a write to this address is reflected in the Error Interrupt Status register if the corresponding bit of the Error Interrupt Status Enable register is set.
This register is applicable for an SD/eMMC/UHS-II mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FORCE_CUR_LMT_ERR [7:7]	FORCE_DATA_END_BIT_ERR [6:6]	FORCE_DATA_CRC_ERR [5:5]	FORCE_DATA_TOUT_ERR [4:4]	FORCE_CMD_IDX_ERR [3:3]	FORCE_CMD_END_BIT_ERR [2:2]	FORCE_CMD_CRC_ERR [1:1]	FORCE_CMD_TOUT_ERR [0:0]

Bits	15	14	13	12	11	10	9	8
Name	FORCE_VENDOR_ERR3 [15:15]	FORCE_VENDOR_ERR2 [14:14]	FORCE_VENDOR_ERR1 [13:13]	FORCE_BOOT_ACK_ERR [12:12]	FORCE_RESP_ERR [11:11]	FORCE_TUNING_ERR [10:10]	FORCE_ADMA_ERR [9:9]	FORCE_AUTO_CMD_ERR [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	FORCE_CMD_TOUT_ERR	RW	RW	0	Force Event for Command Timeout Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Command Timeout Error Status is set
1	FORCE_CMD_CRC_ERR	RW	RW	0	Force Event for Command CRC Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Command CRC Error Status is set
2	FORCE_CMD_END_BIT_ERR	RW	RW	0	Force Event for Command End Bit Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Command End Bit Error Status is set
3	FORCE_CMD_IDX_ERR	RW	RW	0	Force Event for Command Index Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Command Index Error Status is set

Bits	Name	SW	HW	Default or Enum	Description
4	FORCE_DATA_TOUT_ERR	RW	RW	0	Force Event for Data Timeout Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Data Timeout Error Status is set
5	FORCE_DATA_CRC_ERR	RW	RW	0	Force Event for Data CRC Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Data CRC Error Status is set
6	FORCE_DATA_END_BIT_ERR	RW	RW	0	Force Event for Data End Bit Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Data End Bit Error Status is set
7	FORCE_CUR_LMT_ERR	RW	RW	0	Force Event for Current Limit Error Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Current Limit Error Status is set
8	FORCE_AUTO_CMD_ERR	RW	RW	0	Force Event for Auto CMD Error (SD/eMMC Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Auto CMD Error Status is set
9	FORCE_ADMA_ERR	RW	RW	0	Force Event for ADMA Error Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): ADMA Error Status is set
10	FORCE_TUNING_ERR	RW	RW	0	Force Event for Tuning Error (UHS-I Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Tuning Error Status is set
11	FORCE_RESP_ERR	RW	RW	0	Force Event for Response Error (SD Mode only) Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Response Error Status is set
12	FORCE_BOOT_ACK_ERR	RW	RW	0	Force Event for Boot Ack error Values: - 0x0 (FALSE): Not Affected - 0x1 (TRUE): Boot ack Error Status is set
13	FORCE_VENDOR_ERR1	RW	RW	0	This bit (FORCE_VENDOR_ERR1) of the FORCE_ERROR_INT_STAT_R register is reserved. It always returns 0.
14	FORCE_VENDOR_ERR2	RW	RW	0	This bit (FORCE_VENDOR_ERR2) of the FORCE_ERROR_INT_STAT_R register is reserved. It always returns 0.
15	FORCE_VENDOR_ERR3	RW	RW	0	This bit (FORCE_VENDOR_ERR3) of the FORCE_ERROR_INT_STAT_R register is reserved. It always returns 0.

25.3.2.34 SDHC_CORE_ADMA_ERR_STAT_R

Description: ADMA Error Status Register

Address: 0x40461054

Offset: 0x54

Retention: Retained

IsDeepSleep: No

Comment: This register stores the ADMA state during an ADMA error. This register is applicable for an SD/eMMC/UHS-II mode.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					ADMA_LEN_ERR [2:2]	ADMA_ERR_STATES [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	ADMA_ERR_STATES	R	R	0	ADMA Error States These bits indicate the state of ADMA when an error occurs during ADMA data transfer. Values: - 0x0 (ST_STOP): Stop DMA - SYS_ADR register points to a location next to the error descriptor - 0x1 (ST_FDS): Fetch Descriptor - SYS_ADR register points to the error descriptor - 0x2 (UNUSED): Never set this state - 0x3 (ST_TFR): Transfer Data - SYS_ADR register points to a location next to the error descriptor
2	ADMA_LEN_ERR	R	R	0	ADMA Length Mismatch Error States This error occurs in the following instances: - While the Block Count Enable is being set, the total data length specified by the Descriptor table is different from that specified by the Block Count and Block Length - When the total data length cannot be divided by the block length Values: - 0x0 (NO_ERR): No Error - 0x1 (ERROR): Error

25.3.2.35 SDHC_CORE_ADMA_SA_LOW_R

Description: ADMA System Address Register - Low
Address: 0x40461058
Offset: 0x58
Retention: Retained
IsDeepSleep: No
Comment: This register holds the lower 32-bit system address for DMA transfer. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADMA_SA_LOW [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADMA_SA_LOW [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADMA_SA_LOW [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADMA_SA_LOW [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADMA_SA_LOW	RW	RW	0	ADMA System Address These bits indicate the lower 32 bits of the ADMA system address. - SDMA: If Host Version 4 Enable is set to 1, this register stores the system address of the data location - ADMA2: This register stores the byte address of the executing command of the descriptor table - ADMA3: This register is set by ADMA3. ADMA2 increments the address of this register that points to the next line, every time a Descriptor line is fetched.

25.3.2.36 SDHC_CORE_ADMA_ID_LOW_R

Description: ADMA3 Integrated Descriptor Address Register - Low
Address: 0x40461078
Offset: 0x78
Retention: Retained
IsDeepSleep: No
Comment: This register holds the lower 32-bit Integrated Descriptor address. This register is applicable for an SD/eMMC/UHS-II mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ADMA_ID_LOW [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	ADMA_ID_LOW [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	ADMA_ID_LOW [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ADMA_ID_LOW [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	ADMA_ID_LOW	RW	RW	0	ADMA Integrated Descriptor Address These bits indicate the lower 32-bit of the ADMA Integrated Descriptor address. The start address of Integrated Descriptor is set to these register bits. The ADMA3 fetches one Descriptor Address and increments these bits to indicate the next Descriptor address.

25.3.2.37 SDHC_CORE_HOST_CNTRL_VERS_R

Description: Host Controller Version
Address: 0x404610FE
Offset: 0xFE
Retention: Retained
IsDeepSleep: No
Comment: This register is used to indicate the Host Controller Version number.
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SPEC_VERSION_NUM [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VENDOR_VERSION_NUM [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SPEC_VERSION_NUM	R	R	5	Specification Version Number These bits indicate the Host controller specification version. The upper and lower 4-bits indicate the version. Values 0x06-0xFF are reserved. Values: - 0x0 (VER_1_00): SD Host Controller Specification Version 1.00 - 0x1 (VER_2_00): SD Host Controller Specification Version 2.00 - 0x2 (VER_3_00): SD Host Controller Specification Version 3.00 - 0x3 (VER_4_00): SD Host Controller Specification Version 4.00 - 0x4 (VER_4_10): SD Host Controller Specification Version 4.10 - 0x5 (VER_4_20): SD Host Controller Specification Version 4.20
8:15	VENDOR_VERSION_NUM	R	R	0	Vendor Version Number This field is reserved for the vendor version number. Host Driver must not use this status.

25.3.2.38 SDHC_CORE_MSHC_VER_ID_R

Description: MSHC version
Address: 0x40461500
Offset: 0x500
Retention: Retained
IsDeepSleep: No
Comment: This register reflects the current release number of DWC_mshc/DWC_mshc_lite.
Default: 0x3137302A

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MSHC_VER_ID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MSHC_VER_ID [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MSHC_VER_ID [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MSHC_VER_ID [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	MSHC_VER_ID	R	R	825700394	Current release number This field indicates the Synopsys DesignWare Cores DWC_mshc/DWC_mshc_lite current release number that is read by an application. For example, release number '1.60a' is represented in ASCII as 0x313630. Lower 8 bits read from this register can be ignored by the application. An application reading this register in conjunction with the MSHC_VER_TYPE_R register, gathers details of the current release.

25.3.2.39 SDHC_CORE_MSHC_VER_TYPE_R

Description: MSHC version type
Address: 0x40461504
Offset: 0x504
Retention: Retained
IsDeepSleep: No
Comment: This register reflects the current release type of DWC_mshc/DWC_mshc_lite.
Default: 0x67612A2A

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	MSHC_VER_TYPE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MSHC_VER_TYPE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MSHC_VER_TYPE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MSHC_VER_TYPE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	MSHC_VER_TYPE	R	R	1734421034	Current release type This field indicates the Synopsys DesignWare Cores DWC_mshc/DWC_mshc_lite current release type that is read by an application. For example, release type is 'ga' is represented in ASCII as 0x6761. Lower 16 bits read from this register can be ignored by the application. An application reading this register in conjunction with the MSHC_VER_ID_R register, gathers details of the current release.

25.3.2.40 SDHC_CORE_MSHC_CTRL_R

Description: MSHC Control register
Address: 0x40461508
Offset: 0x508
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control the operation of MSHC Host Controller.
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SW_CG_DIS [4:4]	None [3:1]			CMD_CONFLICT_CHECK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CMD_CONFLICT_CHECK	RW	RW	1	Command conflict check This bit enables command conflict check. Note: DWC_mshc controller monitors the CMD line whenever a command is issued and checks whether the value driven on sd_cmd_out matches the value on sd_cmd_in at next subsequent edge of cclk_tx to determine command conflict error. This bit is cleared only if the feed back delay (including IO Pad delay) is more than (t_card_clk_period - t_setup), where t_setup is the setup time of a flop in DWC_mshc. The I/O pad delay is consistent across CMD and DATA lines, and it is within the value: (2*t_card_clk_period - t_setup) Values: - 0x0 (DISABLE_CMD_CONFLICT_CHK): Disable command conflict check - 0x1 (CMD_CONFLICT_CHK_LAT1): Check for command conflict after 1 card clock cycle

Bits	Name	SW	HW	Default or Enum	Description
4	SW_CG_DIS	RW	RW	0	Internal clock gating disable control This bit must be used to disable IP's internal clock gating when required. when disabled clocks are not gated. Clocks to the core (except hclk) must be stopped when programming this bit. Values: - 0x0 (ENABLE): Internal clock gates are active and clock gating is controlled internally - 0x1 (DISABLE): Internal clock gating is disabled, clocks are not gated internally

25.3.2.41 SDHC_CORE_MBIU_CTRL_R

Description: MBIU Control register

Address: 0x40461510

Offset: 0x510

Retention: Retained

IsDeepSleep: No

Comment: This register is used to select the valid burst types that the AHB Master bus interface can generate. When more than one bit is set the master selects the burst it prefers among those that are enabled in this register.

Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				BURST_INCR16_EN [3:3]	BURST_INCR8_EN [2:2]	BURST_INCR4_EN [1:1]	UNDEFL_INCR_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	UNDEFL_INCR_EN	RW	RW	1	Undefined INCR Burst Controls generation of undefined length INCR transfer on Master interface. Values: - 0x0 (FALSE): Undefined INCR type burst is the least preferred burst on AHB Master I/F - 0x1 (TRUE): Undefined INCR type burst is the most preferred burst on AHB Master I/F
1	BURST_INCR4_EN	RW	RW	0	INCR4 Burst Controls generation of INCR4 transfers on Master interface. Values: - 0x0 (FALSE): AHB INCR4 burst type is not generated on Master I/F - 0x1 (TRUE): AHB INCR4 burst type can be generated on Master I/F
2	BURST_INCR8_EN	RW	RW	0	INCR8 Burst Controls generation of INCR8 transfers on Master interface. Values: - 0x0 (FALSE): AHB INCR8 burst type is not generated on Master I/F - 0x1 (TRUE): AHB INCR8 burst type can be generated on Master I/F

Bits	Name	SW	HW	Default or Enum	Description
3	BURST_INCR16_EN	RW	RW	0	INCR16 Burst Controls generation of INCR16 transfers on Master interface. Values: - 0x0 (FALSE): AHB INCR16 burst type is not generated on Master I/F - 0x1 (TRUE): AHB INCR16 burst type can be generated on Master I/F

25.3.2.42 SDHC_CORE_EMMC_CTRL_R

Description: eMMC Control register
Address: 0x4046152C
Offset: 0x52C
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control the eMMC operation.
Default: 0xC

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				EMMC _RST_N _OE [3:3]	EMMC _RST_N [2:2]	DISABLE _DATA _CRC_CHK [1:1]	CARD_IS _EMMC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CQE _PREFE _TCH _DISABLE [10:10]	CQE _ALGO _SEL [9:9]	None [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CARD_IS_EMMC	RW	RW	0	eMMC Card present This bit indicates the type of card connected. An application program this bit based on the card connected to SDHC. Values: - 0x1 (EMMC_CARD): Card connected to SDHC is an eMMC card - 0x0 (NON_EMMC_CARD): Card connected to SDHC is a non-eMMC card
1	DISABLE_DATA_CRC_CHK	RW	RW	0	Disable Data CRC Check This bit controls masking of CRC16 error for Card Write in eMMC mode. This is useful in bus testing (CMD19) for an eMMC device. In bus testing, an eMMC card does not send CRC status for a block, which may generate CRC error. This CRC error can be masked using this bit during bus testing. Values: - 0x1 (DISABLE): DATA CRC check is disabled - 0x0 (ENABLE): DATA CRC check is enabled

Bits	Name	SW	HW	Default or Enum	Description
2	EMMC_RST_N	RW	RW	1	EMMC Device Reset signal control. This register field controls the card_emmc_reset_n output of SDHC Values: - 0x1 (RST_DEASSERT): Reset to eMMC device is deasserted - 0x0 (RST_ASSERT): Reset to eMMC device asserted (active low)
3	EMMC_RST_N_OE	RW	RW	1	Output Enable (OE) control for EMMC Device Reset signal (card_emmc_reset_n). Values: - 0x1 (ENABLE): OE for card_emmc_reset_n is 1 - 0x0 (DISABLE): OE for card_emmc_reset_n is 0
9	CQE_ALGO_SEL	RW	RW	0	Scheduler algorithm selected for execution This bit selects the Algorithm used for selecting one of the many ready tasks for execution. Values: - 0x0 (PRI_REORDER_PLUS_FCFS): Priority based reordering with FCFS to resolve equal priority tasks - 0x1 (FCFS_ONLY): First come First serve, in the order of DBR rings
10	CQE_PREFETCH_DISABLE	RW	RW	0	Enable or Disable CQE's PREFETCH feature This field allows Software to disable CQE's data prefetch feature when set to 1. Values: - 0x0 (PREFETCH_ENABLE): CQE can Prefetch data for successive WRITE transfers and pipeline successive READ transfers - 0x1 (PREFETCH_DISABLE): Prefetch for WRITE and Pipeline for READ are disabled

25.3.2.43 SDHC_CORE_BOOT_CTRL_R

Description: eMMC Boot Control register
Address: 0x4046152E
Offset: 0x52E
Retention: Retained
IsDeepSleep: No
Comment: This register is used to control the eMMC Boot operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALIDATE_BOOT [7:7]	None [6:1]						MAN_BOOT_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	BOOT_TOUT_CNT [15:12]				None [11:9]			BOOT_ACK_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	MAN_BOOT_EN	RW	RW	0	Mandatory Boot Enable This bit is used to initiate the mandatory boot operation. The application sets this bit along with VALIDATE_BOOT bit. Writing 0 is ignored. The SDHC clears this bit after the boot transfer is completed or terminated. Values: - 0x1 (MAN_BOOT_EN): Mandatory boot enable - 0x0 (MAN_BOOT_DIS): Mandatory boot disable
7	VALIDATE_BOOT	W	W	0	Validate Mandatory Boot Enable bit This bit is used to validate the MAN_BOOT_EN bit. Values: - 0x1 (TRUE): Validate Mandatory boot enable bit - 0x0 (FALSE): Ignore Mandatory boot Enable bit
8	BOOT_ACK_ENABLE	RW	RW	0	Boot Acknowledge Enable When this bit set, SDHC checks for boot acknowledge start pattern of 0-1-0 during boot operation. This bit is applicable for both mandatory and alternate boot mode. Values: - 0x1 (TRUE): Boot Ack enable - 0x0 (FALSE): Boot Ack disable

Bits	Name	SW	HW	Default or Enum	Description
12:15	BOOT_TOUT_CNT	RW	RW	0	Boot Ack Timeout Counter Value. This value determines the interval by which boot ack timeout (50 ms) is detected when boot ack is expected during boot operation. - 0xF - Reserved - 0xE - TMCLK x 2 ²⁷ - .. - - 0x1 - TMCLK x 2 ¹⁴ - 0x0 - TMCLK x 2 ¹³

25.3.2.44 SDHC_CORE_GP_IN_R

Description: General Purpose Input register
Address: 0x40461530
Offset: 0x530
Retention: Retained
IsDeepSleep: No
Comment: This register is used as a general purpose input register. This register stores all the inputs sampled from input port gp_in.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							GP_IN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	GP_IN	R	R	0	It reflects the value of gp_in ports. NOT USED - ALWAYS READS 0

25.3.2.45 SDHC_CORE_GP_OUT_R

Description: General Purpose Output register
Address: 0x40461534
Offset: 0x534
Retention: Retained
IsDeepSleep: No
Comment: This register is used as a general purpose output register. The contents of this register are reflected on the output port gp_out.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CARD_CLOCK_OUT_DLY [7:6]		IO_VOLT_SEL_OE [5:5]	CARD_IF_PWR_EN_OE [4:4]	CARD_CLOCK_OE [3:3]	LED_CTRL_OE [2:2]	CARD_MECH_WRITE_PROT_EN [1:1]	CARD_DETECT_EN [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						CARD_CLOCK_IN_DLY [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CARD_DETECT_EN	RW	RW	0	0: Force card_detect_n input to 0 1: Normal card_detect_n operation allowing card detection from a device pin
1	CARD_MECH_WRITE_PROT_EN	RW	RW	0	card_mech_write_prot, despite its name, is an active low signal (per the SD Host Controller Standard spec it is officially called SDWP#). Consider that in the following: 0: Force card_mech_write_prot input to 0 internally; this forces write protection to be active 1: Allow card_mech_write_prot to work normally per the device's pin state
2	LED_CTRL_OE	RW	RW	0	Active high output enable for the LED output signal (led_ctrl) controlled through HOST_CTRL1_R.LED_CTRL: 0: disable OE associated with the led_ctrl output 1: enable OE associated with the led_ctrl output
3	CARD_CLOCK_OE	RW	RW	0	Active high output enable for the card clock output (clk_card) which is gated by CLK_CTRL_R.SD_CLK_EN: 0: disable OE to the clk_card output 1: enable OE to the clk_card output
4	CARD_IF_PWR_EN_OE	RW	RW	0	Active high output enable for the card interface power enable output (card_if_pwr_en) controlled through PWR_CTRL_R.SD_BUS_PWR_VDD1: 0: disable OE to the card_if_pwr_en output 1: enable OE to the card_if_pwr_en output

Bits	Name	SW	HW	Default or Enum	Description
5	IO_VOLT_SEL_OE	RW	RW	0	Active high output enable for the IO voltage selection signal (io_volt_sel) controlled through HOST_CTRL_2.SIGNALING_EN: 0: disable OE to the io_volt_sel output 1: enable OE to the io_volt_sel output
6:7	CARD_CLOCK_OUT_DLY	RW	RW	0	Delay CARD_CLOCK output relative to CMD/DAT to meet output setup/hold times; set according to interface mode: 00: SD Default Speed, SD High Speed, SD SDR12, eMMC Legacy 01: SD SDR25, SD SDR50, eMMC High Speed SDR 10: RESERVED 11: SD DDR50, eMMC DDR
8:9	CARD_CLOCK_IN_DLY	RW	RW	0	Delay CARD_CLOCK input internally to optimally sample CMD/DAT; set according to interface mode: 00: SD Default Speed, SD SDR12, eMMC Legacy 01: SD SDR25, SD SDR50 10: SD High Speed, eMMC High Speed SDR 11: SD DDR50, eMMC DDR

26 SFLASH

Description FLASH Supervisory Region
Base Address 0x17000000
Size 0x8000
Slave Num MEMORYMAP

Register Name	Address	Permission	Description
SFLASH_SI_REVISION_ID	0x17000001	FULL	Indicates Silicon Revision ID of the device
SFLASH_SILICON_ID	0x17000002	FULL	Indicates Silicon ID of the device
SFLASH_SFLASH_SVN	0x170000A8	FULL	SFLASH Subversion
SFLASH_FB_FLAGS	0x170001FC	FULL	Flash boot flags
SFLASH_EPASS_TEMP_TRIM_TEMP_ROOMSORT	0x1700064E	FULL	On Chip temperature measured using external currents and external ADC at ROOM
SFLASH_EPASS_TEMP_TRIM_DIODE_ROOMSORT	0x17000650	FULL	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at ROOM
SFLASH_EPASS_TEMP_TRIM_VBG_ROOMSORT	0x17000652	FULL	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at ROOM
SFLASH_EPASS_TEMP_TRIM_TEMP_COLDSORT	0x17000654	FULL	On Chip temperature measured using external currents and external ADC at COLD
SFLASH_EPASS_TEMP_TRIM_DIODE_COLDSORT	0x17000656	FULL	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at COLD
SFLASH_EPASS_TEMP_TRIM_VBG_COLDSORT	0x17000658	FULL	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at COLD
SFLASH_EPASS_TEMP_TRIM_TEMP_HOTCLASS	0x1700065A	FULL	On Chip temperature measured using external currents and external ADC at HOT
SFLASH_EPASS_TEMP_TRIM_DIODE_HOTCLASS	0x1700065C	FULL	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at HOT
SFLASH_EPASS_TEMP_TRIM_VBG_HOTCLASS	0x1700065E	FULL	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at HOT
SFLASH_EPASS_TEMP_TRIM_DIODE_ROOMSORT_5V	0x1700066A	FULL	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at ROOM
SFLASH_EPASS_TEMP_TRIM_VBG_ROOMSORT_5V	0x1700066C	FULL	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at ROOM
SFLASH_EPASS_TEMP_TRIM_DIODE_COLDSORT_5V	0x1700066E	FULL	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at COLD
SFLASH_EPASS_TEMP_TRIM_VBG_COLDSORT_5V	0x17000670	FULL	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at COLD
SFLASH_EPASS_TEMP_TRIM_DIODE_HOTCLASS_5V	0x17000672	FULL	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at HOT
SFLASH_EPASS_TEMP_TRIM_VBG_HOTCLASS_5V	0x17000674	FULL	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at HOT
SFLASH_SRSS_PWR_OFFSET	0x17000730	FULL	SRSS_PWR_OFFSET
SFLASH_SRSS_PWR_TRIM_HT_PWRSYS_INTERNAL	0x17000734	FULL	Trim settings when the supply is intended to come from the internal regulators
SFLASH_SRSS_PWR_TRIM_HT_PWRSYS_EXTERNAL	0x17000738	FULL	Trim settings for the regulators so they do not interfere with external supply
SFLASH_USER_FREE_ROW00	0x17000800	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW01	0x17000804	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW02	0x17000808	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW03	0x1700080C	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW04	0x17000810	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW05	0x17000814	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW06	0x17000818	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW07	0x1700081C	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW08	0x17000820	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW09	0x17000824	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW010	0x17000828	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW011	0x1700082C	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW012	0x17000830	FULL	USER_FREE_ROW0
SFLASH_USER_FREE_ROW013	0x17000834	FULL	USER_FREE_ROW0

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW014	0x17000838	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW015	0x1700083C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW016	0x17000840	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW017	0x17000844	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW018	0x17000848	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW019	0x1700084C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW020	0x17000850	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW021	0x17000854	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW022	0x17000858	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW023	0x1700085C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW024	0x17000860	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW025	0x17000864	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW026	0x17000868	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW027	0x1700086C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW028	0x17000870	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW029	0x17000874	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW030	0x17000878	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW031	0x1700087C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW032	0x17000880	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW033	0x17000884	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW034	0x17000888	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW035	0x1700088C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW036	0x17000890	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW037	0x17000894	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW038	0x17000898	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW039	0x1700089C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW040	0x170008A0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW041	0x170008A4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW042	0x170008A8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW043	0x170008AC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW044	0x170008B0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW045	0x170008B4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW046	0x170008B8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW047	0x170008BC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW048	0x170008C0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW049	0x170008C4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW050	0x170008C8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW051	0x170008CC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW052	0x170008D0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW053	0x170008D4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW054	0x170008D8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW055	0x170008DC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW056	0x170008E0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW057	0x170008E4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW058	0x170008E8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW059	0x170008EC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW060	0x170008F0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW061	0x170008F4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW062	0x170008F8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW063	0x170008FC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW064	0x17000900	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW065	0x17000904	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW066	0x17000908	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW067	0x1700090C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW068	0x17000910	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW069	0x17000914	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW070	0x17000918	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW071	0x1700091C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW072	0x17000920	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW073	0x17000924	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW074	0x17000928	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW075	0x1700092C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW076	0x17000930	FULL	USER FREE ROW0

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW077	0x17000934	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW078	0x17000938	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW079	0x1700093C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW080	0x17000940	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW081	0x17000944	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW082	0x17000948	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW083	0x1700094C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW084	0x17000950	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW085	0x17000954	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW086	0x17000958	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW087	0x1700095C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW088	0x17000960	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW089	0x17000964	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW090	0x17000968	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW091	0x1700096C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW092	0x17000970	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW093	0x17000974	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW094	0x17000978	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW095	0x1700097C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW096	0x17000980	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW097	0x17000984	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW098	0x17000988	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW099	0x1700098C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW100	0x17000990	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW101	0x17000994	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW102	0x17000998	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW103	0x1700099C	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW104	0x170009A0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW105	0x170009A4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW106	0x170009A8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW107	0x170009AC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW108	0x170009B0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW109	0x170009B4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW110	0x170009B8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW111	0x170009BC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW112	0x170009C0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW113	0x170009C4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW114	0x170009C8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW115	0x170009CC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW116	0x170009D0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW117	0x170009D4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW118	0x170009D8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW119	0x170009DC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW120	0x170009E0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW121	0x170009E4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW122	0x170009E8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW123	0x170009EC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW124	0x170009F0	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW125	0x170009F4	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW126	0x170009F8	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW127	0x170009FC	FULL	USER FREE ROW0
SFLASH_USER_FREE_ROW10	0x17000A00	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW11	0x17000A04	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW12	0x17000A08	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW13	0x17000A0C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW14	0x17000A10	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW15	0x17000A14	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW16	0x17000A18	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW17	0x17000A1C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW18	0x17000A20	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW19	0x17000A24	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW110	0x17000A28	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW111	0x17000A2C	FULL	USER FREE ROW1

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW112	0x17000A30	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW113	0x17000A34	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW114	0x17000A38	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW115	0x17000A3C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW116	0x17000A40	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW117	0x17000A44	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW118	0x17000A48	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW119	0x17000A4C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW120	0x17000A50	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW121	0x17000A54	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW122	0x17000A58	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW123	0x17000A5C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW124	0x17000A60	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW125	0x17000A64	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW126	0x17000A68	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW127	0x17000A6C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW128	0x17000A70	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW129	0x17000A74	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW130	0x17000A78	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW131	0x17000A7C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW132	0x17000A80	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW133	0x17000A84	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW134	0x17000A88	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW135	0x17000A8C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW136	0x17000A90	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW137	0x17000A94	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW138	0x17000A98	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW139	0x17000A9C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW140	0x17000AA0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW141	0x17000AA4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW142	0x17000AA8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW143	0x17000AAC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW144	0x17000AB0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW145	0x17000AB4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW146	0x17000AB8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW147	0x17000ABC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW148	0x17000AC0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW149	0x17000AC4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW150	0x17000AC8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW151	0x17000ACC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW152	0x17000AD0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW153	0x17000AD4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW154	0x17000AD8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW155	0x17000ADC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW156	0x17000AE0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW157	0x17000AE4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW158	0x17000AE8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW159	0x17000AEC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW160	0x17000AF0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW161	0x17000AF4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW162	0x17000AF8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW163	0x17000AFC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW164	0x17000B00	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW165	0x17000B04	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW166	0x17000B08	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW167	0x17000B0C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW168	0x17000B10	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW169	0x17000B14	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW170	0x17000B18	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW171	0x17000B1C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW172	0x17000B20	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW173	0x17000B24	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW174	0x17000B28	FULL	USER FREE ROW1

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW175	0x17000B2C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW176	0x17000B30	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW177	0x17000B34	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW178	0x17000B38	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW179	0x17000B3C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW180	0x17000B40	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW181	0x17000B44	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW182	0x17000B48	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW183	0x17000B4C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW184	0x17000B50	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW185	0x17000B54	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW186	0x17000B58	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW187	0x17000B5C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW188	0x17000B60	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW189	0x17000B64	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW190	0x17000B68	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW191	0x17000B6C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW192	0x17000B70	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW193	0x17000B74	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW194	0x17000B78	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW195	0x17000B7C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW196	0x17000B80	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW197	0x17000B84	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW198	0x17000B88	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW199	0x17000B8C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1100	0x17000B90	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1101	0x17000B94	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1102	0x17000B98	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1103	0x17000B9C	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1104	0x17000BA0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1105	0x17000BA4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1106	0x17000BA8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1107	0x17000BAC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1108	0x17000BB0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1109	0x17000BB4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1110	0x17000BB8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1111	0x17000BBC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1112	0x17000BC0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1113	0x17000BC4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1114	0x17000BC8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1115	0x17000BCC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1116	0x17000BD0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1117	0x17000BD4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1118	0x17000BD8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1119	0x17000BDC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1120	0x17000BE0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1121	0x17000BE4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1122	0x17000BE8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1123	0x17000BEC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1124	0x17000BF0	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1125	0x17000BF4	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1126	0x17000BF8	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW1127	0x17000BFC	FULL	USER FREE ROW1
SFLASH_USER_FREE_ROW20	0x17000C00	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW21	0x17000C04	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW22	0x17000C08	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW23	0x17000C0C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW24	0x17000C10	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW25	0x17000C14	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW26	0x17000C18	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW27	0x17000C1C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW28	0x17000C20	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW29	0x17000C24	FULL	USER FREE ROW2

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW210	0x17000C28	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW211	0x17000C2C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW212	0x17000C30	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW213	0x17000C34	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW214	0x17000C38	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW215	0x17000C3C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW216	0x17000C40	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW217	0x17000C44	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW218	0x17000C48	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW219	0x17000C4C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW220	0x17000C50	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW221	0x17000C54	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW222	0x17000C58	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW223	0x17000C5C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW224	0x17000C60	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW225	0x17000C64	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW226	0x17000C68	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW227	0x17000C6C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW228	0x17000C70	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW229	0x17000C74	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW230	0x17000C78	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW231	0x17000C7C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW232	0x17000C80	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW233	0x17000C84	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW234	0x17000C88	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW235	0x17000C8C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW236	0x17000C90	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW237	0x17000C94	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW238	0x17000C98	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW239	0x17000C9C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW240	0x17000CA0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW241	0x17000CA4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW242	0x17000CA8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW243	0x17000CAC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW244	0x17000CB0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW245	0x17000CB4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW246	0x17000CB8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW247	0x17000CBC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW248	0x17000CC0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW249	0x17000CC4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW250	0x17000CC8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW251	0x17000CCC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW252	0x17000CD0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW253	0x17000CD4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW254	0x17000CD8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW255	0x17000CDC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW256	0x17000CE0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW257	0x17000CE4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW258	0x17000CE8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW259	0x17000CEC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW260	0x17000CF0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW261	0x17000CF4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW262	0x17000CF8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW263	0x17000CFC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW264	0x17000D00	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW265	0x17000D04	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW266	0x17000D08	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW267	0x17000D0C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW268	0x17000D10	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW269	0x17000D14	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW270	0x17000D18	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW271	0x17000D1C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW272	0x17000D20	FULL	USER FREE ROW2

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW273	0x17000D24	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW274	0x17000D28	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW275	0x17000D2C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW276	0x17000D30	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW277	0x17000D34	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW278	0x17000D38	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW279	0x17000D3C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW280	0x17000D40	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW281	0x17000D44	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW282	0x17000D48	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW283	0x17000D4C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW284	0x17000D50	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW285	0x17000D54	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW286	0x17000D58	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW287	0x17000D5C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW288	0x17000D60	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW289	0x17000D64	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW290	0x17000D68	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW291	0x17000D6C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW292	0x17000D70	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW293	0x17000D74	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW294	0x17000D78	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW295	0x17000D7C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW296	0x17000D80	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW297	0x17000D84	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW298	0x17000D88	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW299	0x17000D8C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2100	0x17000D90	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2101	0x17000D94	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2102	0x17000D98	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2103	0x17000D9C	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2104	0x17000DA0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2105	0x17000DA4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2106	0x17000DA8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2107	0x17000DAC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2108	0x17000DB0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2109	0x17000DB4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2110	0x17000DB8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2111	0x17000DBC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2112	0x17000DC0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2113	0x17000DC4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2114	0x17000DC8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2115	0x17000DCC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2116	0x17000DD0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2117	0x17000DD4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2118	0x17000DD8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2119	0x17000DDC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2120	0x17000DE0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2121	0x17000DE4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2122	0x17000DE8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2123	0x17000DEC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2124	0x17000DF0	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2125	0x17000DF4	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2126	0x17000DF8	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW2127	0x17000DFC	FULL	USER FREE ROW2
SFLASH_USER_FREE_ROW30	0x17000E00	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW31	0x17000E04	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW32	0x17000E08	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW33	0x17000E0C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW34	0x17000E10	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW35	0x17000E14	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW36	0x17000E18	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW37	0x17000E1C	FULL	USER FREE ROW3

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW38	0x17000E20	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW39	0x17000E24	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW310	0x17000E28	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW311	0x17000E2C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW312	0x17000E30	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW313	0x17000E34	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW314	0x17000E38	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW315	0x17000E3C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW316	0x17000E40	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW317	0x17000E44	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW318	0x17000E48	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW319	0x17000E4C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW320	0x17000E50	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW321	0x17000E54	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW322	0x17000E58	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW323	0x17000E5C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW324	0x17000E60	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW325	0x17000E64	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW326	0x17000E68	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW327	0x17000E6C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW328	0x17000E70	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW329	0x17000E74	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW330	0x17000E78	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW331	0x17000E7C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW332	0x17000E80	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW333	0x17000E84	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW334	0x17000E88	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW335	0x17000E8C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW336	0x17000E90	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW337	0x17000E94	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW338	0x17000E98	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW339	0x17000E9C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW340	0x17000EA0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW341	0x17000EA4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW342	0x17000EA8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW343	0x17000EAC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW344	0x17000EB0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW345	0x17000EB4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW346	0x17000EB8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW347	0x17000EBC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW348	0x17000EC0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW349	0x17000EC4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW350	0x17000EC8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW351	0x17000ECC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW352	0x17000ED0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW353	0x17000ED4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW354	0x17000ED8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW355	0x17000EDC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW356	0x17000EE0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW357	0x17000EE4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW358	0x17000EE8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW359	0x17000EEC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW360	0x17000EF0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW361	0x17000EF4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW362	0x17000EF8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW363	0x17000EFC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW364	0x17000F00	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW365	0x17000F04	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW366	0x17000F08	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW367	0x17000F0C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW368	0x17000F10	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW369	0x17000F14	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW370	0x17000F18	FULL	USER FREE ROW3

Register Name	Address	Permission	Description
SFLASH_USER_FREE_ROW371	0x17000F1C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW372	0x17000F20	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW373	0x17000F24	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW374	0x17000F28	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW375	0x17000F2C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW376	0x17000F30	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW377	0x17000F34	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW378	0x17000F38	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW379	0x17000F3C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW380	0x17000F40	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW381	0x17000F44	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW382	0x17000F48	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW383	0x17000F4C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW384	0x17000F50	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW385	0x17000F54	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW386	0x17000F58	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW387	0x17000F5C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW388	0x17000F60	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW389	0x17000F64	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW390	0x17000F68	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW391	0x17000F6C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW392	0x17000F70	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW393	0x17000F74	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW394	0x17000F78	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW395	0x17000F7C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW396	0x17000F80	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW397	0x17000F84	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW398	0x17000F88	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW399	0x17000F8C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3100	0x17000F90	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3101	0x17000F94	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3102	0x17000F98	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3103	0x17000F9C	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3104	0x17000FA0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3105	0x17000FA4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3106	0x17000FA8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3107	0x17000FAC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3108	0x17000FB0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3109	0x17000FB4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3110	0x17000FB8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3111	0x17000FBC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3112	0x17000FC0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3113	0x17000FC4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3114	0x17000FC8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3115	0x17000FCC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3116	0x17000FD0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3117	0x17000FD4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3118	0x17000FD8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3119	0x17000FDC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3120	0x17000FE0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3121	0x17000FE4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3122	0x17000FE8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3123	0x17000FEC	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3124	0x17000FF0	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3125	0x17000FF4	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3126	0x17000FF8	FULL	USER FREE ROW3
SFLASH_USER_FREE_ROW3127	0x17000FFC	FULL	USER FREE ROW3
SFLASH_SFLASH_UPDATE_MARKER0	0x17001800	FULL	Markers for storing SFLASH programming states
SFLASH_SFLASH_UPDATE_MARKER1	0x17001804	FULL	Markers for storing SFLASH programming states
SFLASH_FLASH_BOOT_OBJECT_SIZE	0x17002000	FULL	Flash Boot - Object Size
SFLASH_FLASH_BOOT_APP_ID	0x17002004	FULL	Flash Boot - Application ID/Version
SFLASH_FLASH_BOOT_VERSION_LOW	0x17002018	FULL	Flash Boot - Version Low
SFLASH_FLASH_BOOT_FAMILY_ID	0x1700201C	FULL	Flash Boot - Family ID

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY0	0x17006400	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1	0x17006401	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2	0x17006402	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3	0x17006403	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY4	0x17006404	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY5	0x17006405	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY6	0x17006406	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY7	0x17006407	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY8	0x17006408	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY9	0x17006409	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY10	0x1700640A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY11	0x1700640B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY12	0x1700640C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY13	0x1700640D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY14	0x1700640E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY15	0x1700640F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY16	0x17006410	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY17	0x17006411	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY18	0x17006412	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY19	0x17006413	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY20	0x17006414	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY21	0x17006415	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY22	0x17006416	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY23	0x17006417	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY24	0x17006418	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY25	0x17006419	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY26	0x1700641A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY27	0x1700641B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY28	0x1700641C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY29	0x1700641D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY30	0x1700641E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY31	0x1700641F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY32	0x17006420	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY33	0x17006421	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY34	0x17006422	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY35	0x17006423	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY36	0x17006424	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY37	0x17006425	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY38	0x17006426	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY39	0x17006427	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY40	0x17006428	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY41	0x17006429	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY42	0x1700642A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY43	0x1700642B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY44	0x1700642C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY45	0x1700642D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY46	0x1700642E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY47	0x1700642F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY48	0x17006430	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY49	0x17006431	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY50	0x17006432	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY51	0x17006433	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY52	0x17006434	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY53	0x17006435	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY54	0x17006436	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY55	0x17006437	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY56	0x17006438	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY57	0x17006439	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY58	0x1700643A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY59	0x1700643B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY60	0x1700643C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY61	0x1700643D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY62	0x1700643E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY63	0x1700643F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY64	0x17006440	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY65	0x17006441	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY66	0x17006442	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY67	0x17006443	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY68	0x17006444	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY69	0x17006445	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY70	0x17006446	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY71	0x17006447	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY72	0x17006448	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY73	0x17006449	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY74	0x1700644A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY75	0x1700644B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY76	0x1700644C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY77	0x1700644D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY78	0x1700644E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY79	0x1700644F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY80	0x17006450	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY81	0x17006451	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY82	0x17006452	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY83	0x17006453	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY84	0x17006454	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY85	0x17006455	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY86	0x17006456	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY87	0x17006457	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY88	0x17006458	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY89	0x17006459	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY90	0x1700645A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY91	0x1700645B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY92	0x1700645C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY93	0x1700645D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY94	0x1700645E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY95	0x1700645F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY96	0x17006460	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY97	0x17006461	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY98	0x17006462	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY99	0x17006463	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY100	0x17006464	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY101	0x17006465	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY102	0x17006466	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY103	0x17006467	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY104	0x17006468	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY105	0x17006469	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY106	0x1700646A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY107	0x1700646B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY108	0x1700646C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY109	0x1700646D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY110	0x1700646E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY111	0x1700646F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY112	0x17006470	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY113	0x17006471	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY114	0x17006472	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY115	0x17006473	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY116	0x17006474	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY117	0x17006475	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY118	0x17006476	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY119	0x17006477	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY120	0x17006478	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY121	0x17006479	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY122	0x1700647A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY123	0x1700647B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY124	0x1700647C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY125	0x1700647D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY126	0x1700647E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY127	0x1700647F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY128	0x17006480	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY129	0x17006481	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY130	0x17006482	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY131	0x17006483	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY132	0x17006484	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY133	0x17006485	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY134	0x17006486	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY135	0x17006487	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY136	0x17006488	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY137	0x17006489	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY138	0x1700648A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY139	0x1700648B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY140	0x1700648C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY141	0x1700648D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY142	0x1700648E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY143	0x1700648F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY144	0x17006490	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY145	0x17006491	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY146	0x17006492	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY147	0x17006493	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY148	0x17006494	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY149	0x17006495	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY150	0x17006496	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY151	0x17006497	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY152	0x17006498	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY153	0x17006499	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY154	0x1700649A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY155	0x1700649B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY156	0x1700649C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY157	0x1700649D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY158	0x1700649E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY159	0x1700649F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY160	0x170064A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY161	0x170064A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY162	0x170064A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY163	0x170064A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY164	0x170064A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY165	0x170064A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY166	0x170064A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY167	0x170064A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY168	0x170064A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY169	0x170064A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY170	0x170064AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY171	0x170064AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY172	0x170064AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY173	0x170064AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY174	0x170064AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY175	0x170064AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY176	0x170064B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY177	0x170064B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY178	0x170064B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY179	0x170064B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY180	0x170064B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY181	0x170064B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY182	0x170064B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY183	0x170064B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY184	0x170064B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY185	0x170064B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY186	0x170064BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY187	0x170064BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY188	0x170064BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY189	0x170064BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY190	0x170064BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY191	0x170064BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY192	0x170064C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY193	0x170064C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY194	0x170064C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY195	0x170064C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY196	0x170064C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY197	0x170064C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY198	0x170064C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY199	0x170064C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY200	0x170064C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY201	0x170064C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY202	0x170064CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY203	0x170064CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY204	0x170064CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY205	0x170064CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY206	0x170064CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY207	0x170064CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY208	0x170064D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY209	0x170064D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY210	0x170064D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY211	0x170064D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY212	0x170064D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY213	0x170064D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY214	0x170064D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY215	0x170064D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY216	0x170064D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY217	0x170064D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY218	0x170064DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY219	0x170064DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY220	0x170064DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY221	0x170064DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY222	0x170064DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY223	0x170064DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY224	0x170064E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY225	0x170064E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY226	0x170064E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY227	0x170064E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY228	0x170064E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY229	0x170064E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY230	0x170064E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY231	0x170064E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY232	0x170064E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY233	0x170064E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY234	0x170064EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY235	0x170064EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY236	0x170064EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY237	0x170064ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY238	0x170064EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY239	0x170064EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY240	0x170064F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY241	0x170064F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY242	0x170064F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY243	0x170064F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY244	0x170064F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY245	0x170064F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY246	0x170064F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY247	0x170064F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY248	0x170064F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY249	0x170064F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY250	0x170064FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY251	0x170064FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY252	0x170064FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY253	0x170064FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY254	0x170064FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY255	0x170064FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY256	0x17006500	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY257	0x17006501	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY258	0x17006502	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY259	0x17006503	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY260	0x17006504	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY261	0x17006505	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY262	0x17006506	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY263	0x17006507	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY264	0x17006508	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY265	0x17006509	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY266	0x1700650A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY267	0x1700650B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY268	0x1700650C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY269	0x1700650D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY270	0x1700650E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY271	0x1700650F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY272	0x17006510	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY273	0x17006511	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY274	0x17006512	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY275	0x17006513	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY276	0x17006514	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY277	0x17006515	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY278	0x17006516	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY279	0x17006517	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY280	0x17006518	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY281	0x17006519	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY282	0x1700651A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY283	0x1700651B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY284	0x1700651C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY285	0x1700651D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY286	0x1700651E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY287	0x1700651F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY288	0x17006520	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY289	0x17006521	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY290	0x17006522	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY291	0x17006523	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY292	0x17006524	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY293	0x17006525	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY294	0x17006526	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY295	0x17006527	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY296	0x17006528	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY297	0x17006529	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY298	0x1700652A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY299	0x1700652B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY300	0x1700652C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY301	0x1700652D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY302	0x1700652E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY303	0x1700652F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY304	0x17006530	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY305	0x17006531	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY306	0x17006532	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY307	0x17006533	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY308	0x17006534	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY309	0x17006535	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY310	0x17006536	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY311	0x17006537	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY312	0x17006538	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY313	0x17006539	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY314	0x1700653A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY315	0x1700653B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY316	0x1700653C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY317	0x1700653D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY318	0x1700653E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY319	0x1700653F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY320	0x17006540	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY321	0x17006541	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY322	0x17006542	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY323	0x17006543	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY324	0x17006544	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY325	0x17006545	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY326	0x17006546	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY327	0x17006547	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY328	0x17006548	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY329	0x17006549	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY330	0x1700654A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY331	0x1700654B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY332	0x1700654C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY333	0x1700654D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY334	0x1700654E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY335	0x1700654F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY336	0x17006550	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY337	0x17006551	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY338	0x17006552	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY339	0x17006553	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY340	0x17006554	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY341	0x17006555	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY342	0x17006556	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY343	0x17006557	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY344	0x17006558	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY345	0x17006559	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY346	0x1700655A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY347	0x1700655B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY348	0x1700655C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY349	0x1700655D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY350	0x1700655E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY351	0x1700655F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY352	0x17006560	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY353	0x17006561	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY354	0x17006562	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY355	0x17006563	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY356	0x17006564	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY357	0x17006565	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY358	0x17006566	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY359	0x17006567	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY360	0x17006568	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY361	0x17006569	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY362	0x1700656A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY363	0x1700656B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY364	0x1700656C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY365	0x1700656D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY366	0x1700656E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY367	0x1700656F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY368	0x17006570	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY369	0x17006571	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY370	0x17006572	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY371	0x17006573	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY372	0x17006574	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY373	0x17006575	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY374	0x17006576	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY375	0x17006577	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY376	0x17006578	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY377	0x17006579	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY378	0x1700657A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY379	0x1700657B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY380	0x1700657C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY381	0x1700657D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY382	0x1700657E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY383	0x1700657F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY384	0x17006580	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY385	0x17006581	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY386	0x17006582	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY387	0x17006583	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY388	0x17006584	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY389	0x17006585	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY390	0x17006586	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY391	0x17006587	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY392	0x17006588	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY393	0x17006589	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY394	0x1700658A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY395	0x1700658B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY396	0x1700658C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY397	0x1700658D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY398	0x1700658E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY399	0x1700658F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY400	0x17006590	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY401	0x17006591	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY402	0x17006592	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY403	0x17006593	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY404	0x17006594	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY405	0x17006595	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY406	0x17006596	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY407	0x17006597	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY408	0x17006598	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY409	0x17006599	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY410	0x1700659A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY411	0x1700659B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY412	0x1700659C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY413	0x1700659D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY414	0x1700659E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY415	0x1700659F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY416	0x170065A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY417	0x170065A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY418	0x170065A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY419	0x170065A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY420	0x170065A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY421	0x170065A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY422	0x170065A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY423	0x170065A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY424	0x170065A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY425	0x170065A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY426	0x170065AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY427	0x170065AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY428	0x170065AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY429	0x170065AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY430	0x170065AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY431	0x170065AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY432	0x170065B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY433	0x170065B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY434	0x170065B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY435	0x170065B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY436	0x170065B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY437	0x170065B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY438	0x170065B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY439	0x170065B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY440	0x170065B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY441	0x170065B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY442	0x170065BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY443	0x170065BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY444	0x170065BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY445	0x170065BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY446	0x170065BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY447	0x170065BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY448	0x170065C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY449	0x170065C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY450	0x170065C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY451	0x170065C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY452	0x170065C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY453	0x170065C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY454	0x170065C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY455	0x170065C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY456	0x170065C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY457	0x170065C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY458	0x170065CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY459	0x170065CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY460	0x170065CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY461	0x170065CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY462	0x170065CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY463	0x170065CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY464	0x170065D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY465	0x170065D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY466	0x170065D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY467	0x170065D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY468	0x170065D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY469	0x170065D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY470	0x170065D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY471	0x170065D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY472	0x170065D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY473	0x170065D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY474	0x170065DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY475	0x170065DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY476	0x170065DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY477	0x170065DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY478	0x170065DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY479	0x170065DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY480	0x170065E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY481	0x170065E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY482	0x170065E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY483	0x170065E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY484	0x170065E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY485	0x170065E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY486	0x170065E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY487	0x170065E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY488	0x170065E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY489	0x170065E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY490	0x170065EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY491	0x170065EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY492	0x170065EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY493	0x170065ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY494	0x170065EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY495	0x170065EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY496	0x170065F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY497	0x170065F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY498	0x170065F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY499	0x170065F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY500	0x170065F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY501	0x170065F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY502	0x170065F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY503	0x170065F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY504	0x170065F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY505	0x170065F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY506	0x170065FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY507	0x170065FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY508	0x170065FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY509	0x170065FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY510	0x170065FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY511	0x170065FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY512	0x17006600	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY513	0x17006601	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY514	0x17006602	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY515	0x17006603	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY516	0x17006604	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY517	0x17006605	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY518	0x17006606	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY519	0x17006607	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY520	0x17006608	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY521	0x17006609	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY522	0x1700660A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY523	0x1700660B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY524	0x1700660C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY525	0x1700660D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY526	0x1700660E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY527	0x1700660F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY528	0x17006610	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY529	0x17006611	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY530	0x17006612	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY531	0x17006613	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY532	0x17006614	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY533	0x17006615	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY534	0x17006616	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY535	0x17006617	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY536	0x17006618	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY537	0x17006619	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY538	0x1700661A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY539	0x1700661B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY540	0x1700661C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY541	0x1700661D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY542	0x1700661E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY543	0x1700661F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY544	0x17006620	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY545	0x17006621	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY546	0x17006622	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY547	0x17006623	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY548	0x17006624	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY549	0x17006625	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY550	0x17006626	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY551	0x17006627	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY552	0x17006628	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY553	0x17006629	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY554	0x1700662A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY555	0x1700662B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY556	0x1700662C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY557	0x1700662D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY558	0x1700662E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY559	0x1700662F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY560	0x17006630	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY561	0x17006631	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY562	0x17006632	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY563	0x17006633	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY564	0x17006634	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY565	0x17006635	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY566	0x17006636	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY567	0x17006637	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY568	0x17006638	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY569	0x17006639	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY570	0x1700663A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY571	0x1700663B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY572	0x1700663C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY573	0x1700663D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY574	0x1700663E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY575	0x1700663F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY576	0x17006640	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY577	0x17006641	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY578	0x17006642	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY579	0x17006643	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY580	0x17006644	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY581	0x17006645	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY582	0x17006646	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY583	0x17006647	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY584	0x17006648	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY585	0x17006649	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY586	0x1700664A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY587	0x1700664B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY588	0x1700664C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY589	0x1700664D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY590	0x1700664E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY591	0x1700664F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY592	0x17006650	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY593	0x17006651	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY594	0x17006652	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY595	0x17006653	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY596	0x17006654	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY597	0x17006655	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY598	0x17006656	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY599	0x17006657	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY600	0x17006658	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY601	0x17006659	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY602	0x1700665A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY603	0x1700665B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY604	0x1700665C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY605	0x1700665D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY606	0x1700665E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY607	0x1700665F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY608	0x17006660	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY609	0x17006661	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY610	0x17006662	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY611	0x17006663	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY612	0x17006664	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY613	0x17006665	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY614	0x17006666	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY615	0x17006667	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY616	0x17006668	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY617	0x17006669	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY618	0x1700666A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY619	0x1700666B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY620	0x1700666C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY621	0x1700666D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY622	0x1700666E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY623	0x1700666F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY624	0x17006670	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY625	0x17006671	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY626	0x17006672	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY627	0x17006673	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY628	0x17006674	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY629	0x17006675	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY630	0x17006676	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY631	0x17006677	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY632	0x17006678	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY633	0x17006679	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY634	0x1700667A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY635	0x1700667B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY636	0x1700667C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY637	0x1700667D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY638	0x1700667E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY639	0x1700667F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY640	0x17006680	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY641	0x17006681	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY642	0x17006682	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY643	0x17006683	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY644	0x17006684	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY645	0x17006685	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY646	0x17006686	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY647	0x17006687	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY648	0x17006688	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY649	0x17006689	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY650	0x1700668A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY651	0x1700668B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY652	0x1700668C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY653	0x1700668D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY654	0x1700668E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY655	0x1700668F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY656	0x17006690	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY657	0x17006691	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY658	0x17006692	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY659	0x17006693	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY660	0x17006694	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY661	0x17006695	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY662	0x17006696	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY663	0x17006697	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY664	0x17006698	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY665	0x17006699	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY666	0x1700669A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY667	0x1700669B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY668	0x1700669C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY669	0x1700669D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY670	0x1700669E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY671	0x1700669F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY672	0x170066A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY673	0x170066A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY674	0x170066A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY675	0x170066A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY676	0x170066A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY677	0x170066A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY678	0x170066A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY679	0x170066A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY680	0x170066A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY681	0x170066A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY682	0x170066AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY683	0x170066AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY684	0x170066AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY685	0x170066AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY686	0x170066AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY687	0x170066AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY688	0x170066B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY689	0x170066B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY690	0x170066B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY691	0x170066B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY692	0x170066B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY693	0x170066B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY694	0x170066B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY695	0x170066B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY696	0x170066B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY697	0x170066B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY698	0x170066BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY699	0x170066BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY700	0x170066BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY701	0x170066BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY702	0x170066BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY703	0x170066BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY704	0x170066C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY705	0x170066C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY706	0x170066C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY707	0x170066C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY708	0x170066C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY709	0x170066C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY710	0x170066C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY711	0x170066C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY712	0x170066C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY713	0x170066C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY714	0x170066CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY715	0x170066CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY716	0x170066CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY717	0x170066CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY718	0x170066CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY719	0x170066CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY720	0x170066D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY721	0x170066D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY722	0x170066D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY723	0x170066D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY724	0x170066D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY725	0x170066D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY726	0x170066D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY727	0x170066D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY728	0x170066D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY729	0x170066D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY730	0x170066DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY731	0x170066DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY732	0x170066DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY733	0x170066DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY734	0x170066DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY735	0x170066DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY736	0x170066E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY737	0x170066E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY738	0x170066E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY739	0x170066E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY740	0x170066E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY741	0x170066E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY742	0x170066E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY743	0x170066E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY744	0x170066E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY745	0x170066E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY746	0x170066EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY747	0x170066EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY748	0x170066EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY749	0x170066ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY750	0x170066EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY751	0x170066EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY752	0x170066F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY753	0x170066F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY754	0x170066F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY755	0x170066F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY756	0x170066F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY757	0x170066F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY758	0x170066F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY759	0x170066F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY760	0x170066F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY761	0x170066F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY762	0x170066FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY763	0x170066FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY764	0x170066FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY765	0x170066FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY766	0x170066FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY767	0x170066FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY768	0x17006700	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY769	0x17006701	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY770	0x17006702	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY771	0x17006703	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY772	0x17006704	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY773	0x17006705	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY774	0x17006706	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY775	0x17006707	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY776	0x17006708	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY777	0x17006709	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY778	0x1700670A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY779	0x1700670B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY780	0x1700670C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY781	0x1700670D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY782	0x1700670E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY783	0x1700670F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY784	0x17006710	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY785	0x17006711	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY786	0x17006712	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY787	0x17006713	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY788	0x17006714	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY789	0x17006715	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY790	0x17006716	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY791	0x17006717	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY792	0x17006718	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY793	0x17006719	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY794	0x1700671A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY795	0x1700671B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY796	0x1700671C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY797	0x1700671D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY798	0x1700671E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY799	0x1700671F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY800	0x17006720	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY801	0x17006721	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY802	0x17006722	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY803	0x17006723	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY804	0x17006724	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY805	0x17006725	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY806	0x17006726	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY807	0x17006727	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY808	0x17006728	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY809	0x17006729	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY810	0x1700672A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY811	0x1700672B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY812	0x1700672C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY813	0x1700672D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY814	0x1700672E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY815	0x1700672F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY816	0x17006730	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY817	0x17006731	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY818	0x17006732	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY819	0x17006733	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY820	0x17006734	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY821	0x17006735	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY822	0x17006736	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY823	0x17006737	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY824	0x17006738	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY825	0x17006739	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY826	0x1700673A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY827	0x1700673B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY828	0x1700673C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY829	0x1700673D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY830	0x1700673E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY831	0x1700673F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY832	0x17006740	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY833	0x17006741	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY834	0x17006742	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY835	0x17006743	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY836	0x17006744	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY837	0x17006745	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY838	0x17006746	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY839	0x17006747	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY840	0x17006748	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY841	0x17006749	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY842	0x1700674A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY843	0x1700674B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY844	0x1700674C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY845	0x1700674D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY846	0x1700674E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY847	0x1700674F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY848	0x17006750	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY849	0x17006751	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY850	0x17006752	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY851	0x17006753	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY852	0x17006754	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY853	0x17006755	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY854	0x17006756	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY855	0x17006757	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY856	0x17006758	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY857	0x17006759	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY858	0x1700675A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY859	0x1700675B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY860	0x1700675C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY861	0x1700675D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY862	0x1700675E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY863	0x1700675F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY864	0x17006760	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY865	0x17006761	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY866	0x17006762	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY867	0x17006763	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY868	0x17006764	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY869	0x17006765	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY870	0x17006766	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY871	0x17006767	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY872	0x17006768	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY873	0x17006769	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY874	0x1700676A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY875	0x1700676B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY876	0x1700676C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY877	0x1700676D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY878	0x1700676E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY879	0x1700676F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY880	0x17006770	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY881	0x17006771	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY882	0x17006772	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY883	0x17006773	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY884	0x17006774	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY885	0x17006775	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY886	0x17006776	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY887	0x17006777	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY888	0x17006778	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY889	0x17006779	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY890	0x1700677A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY891	0x1700677B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY892	0x1700677C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY893	0x1700677D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY894	0x1700677E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY895	0x1700677F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY896	0x17006780	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY897	0x17006781	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY898	0x17006782	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY899	0x17006783	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY900	0x17006784	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY901	0x17006785	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY902	0x17006786	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY903	0x17006787	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY904	0x17006788	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY905	0x17006789	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY906	0x1700678A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY907	0x1700678B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY908	0x1700678C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY909	0x1700678D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY910	0x1700678E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY911	0x1700678F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY912	0x17006790	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY913	0x17006791	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY914	0x17006792	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY915	0x17006793	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY916	0x17006794	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY917	0x17006795	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY918	0x17006796	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY919	0x17006797	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY920	0x17006798	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY921	0x17006799	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY922	0x1700679A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY923	0x1700679B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY924	0x1700679C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY925	0x1700679D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY926	0x1700679E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY927	0x1700679F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY928	0x170067A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY929	0x170067A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY930	0x170067A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY931	0x170067A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY932	0x170067A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY933	0x170067A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY934	0x170067A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY935	0x170067A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY936	0x170067A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY937	0x170067A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY938	0x170067AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY939	0x170067AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY940	0x170067AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY941	0x170067AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY942	0x170067AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY943	0x170067AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY944	0x170067B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY945	0x170067B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY946	0x170067B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY947	0x170067B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY948	0x170067B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY949	0x170067B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY950	0x170067B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY951	0x170067B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY952	0x170067B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY953	0x170067B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY954	0x170067BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY955	0x170067BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY956	0x170067BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY957	0x170067BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY958	0x170067BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY959	0x170067BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY960	0x170067C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY961	0x170067C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY962	0x170067C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY963	0x170067C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY964	0x170067C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY965	0x170067C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY966	0x170067C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY967	0x170067C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY968	0x170067C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY969	0x170067C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY970	0x170067CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY971	0x170067CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY972	0x170067CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY973	0x170067CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY974	0x170067CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY975	0x170067CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY976	0x170067D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY977	0x170067D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY978	0x170067D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY979	0x170067D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY980	0x170067D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY981	0x170067D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY982	0x170067D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY983	0x170067D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY984	0x170067D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY985	0x170067D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY986	0x170067DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY987	0x170067DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY988	0x170067DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY989	0x170067DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY990	0x170067DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY991	0x170067DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY992	0x170067E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY993	0x170067E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY994	0x170067E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY995	0x170067E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY996	0x170067E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY997	0x170067E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY998	0x170067E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY999	0x170067E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1000	0x170067E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1001	0x170067E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1002	0x170067EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1003	0x170067EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1004	0x170067EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1005	0x170067ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1006	0x170067EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1007	0x170067EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1008	0x170067F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1009	0x170067F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1010	0x170067F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1011	0x170067F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1012	0x170067F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1013	0x170067F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1014	0x170067F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1015	0x170067F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1016	0x170067F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1017	0x170067F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1018	0x170067FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1019	0x170067FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1020	0x170067FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1021	0x170067FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1022	0x170067FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1023	0x170067FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1024	0x17006800	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1025	0x17006801	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1026	0x17006802	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1027	0x17006803	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1028	0x17006804	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1029	0x17006805	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1030	0x17006806	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1031	0x17006807	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1032	0x17006808	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1033	0x17006809	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1034	0x1700680A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1035	0x1700680B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1036	0x1700680C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1037	0x1700680D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1038	0x1700680E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1039	0x1700680F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1040	0x17006810	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1041	0x17006811	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1042	0x17006812	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1043	0x17006813	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1044	0x17006814	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1045	0x17006815	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1046	0x17006816	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1047	0x17006817	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1048	0x17006818	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1049	0x17006819	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1050	0x1700681A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1051	0x1700681B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1052	0x1700681C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1053	0x1700681D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1054	0x1700681E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1055	0x1700681F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1056	0x17006820	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1057	0x17006821	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1058	0x17006822	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1059	0x17006823	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1060	0x17006824	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1061	0x17006825	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1062	0x17006826	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1063	0x17006827	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1064	0x17006828	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1065	0x17006829	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1066	0x1700682A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1067	0x1700682B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1068	0x1700682C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1069	0x1700682D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1070	0x1700682E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1071	0x1700682F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1072	0x17006830	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1073	0x17006831	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1074	0x17006832	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1075	0x17006833	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1076	0x17006834	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1077	0x17006835	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1078	0x17006836	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1079	0x17006837	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1080	0x17006838	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1081	0x17006839	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1082	0x1700683A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1083	0x1700683B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1084	0x1700683C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1085	0x1700683D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1086	0x1700683E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1087	0x1700683F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1088	0x17006840	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1089	0x17006841	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1090	0x17006842	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1091	0x17006843	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1092	0x17006844	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1093	0x17006845	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1094	0x17006846	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1095	0x17006847	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1096	0x17006848	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1097	0x17006849	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1098	0x1700684A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1099	0x1700684B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1100	0x1700684C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1101	0x1700684D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1102	0x1700684E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1103	0x1700684F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1104	0x17006850	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1105	0x17006851	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1106	0x17006852	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1107	0x17006853	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1108	0x17006854	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1109	0x17006855	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1110	0x17006856	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1111	0x17006857	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1112	0x17006858	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1113	0x17006859	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1114	0x1700685A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1115	0x1700685B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1116	0x1700685C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1117	0x1700685D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1118	0x1700685E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1119	0x1700685F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1120	0x17006860	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1121	0x17006861	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1122	0x17006862	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1123	0x17006863	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1124	0x17006864	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1125	0x17006865	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1126	0x17006866	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1127	0x17006867	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1128	0x17006868	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1129	0x17006869	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1130	0x1700686A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1131	0x1700686B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1132	0x1700686C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1133	0x1700686D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1134	0x1700686E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1135	0x1700686F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1136	0x17006870	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1137	0x17006871	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1138	0x17006872	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1139	0x17006873	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1140	0x17006874	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1141	0x17006875	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1142	0x17006876	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1143	0x17006877	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1144	0x17006878	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1145	0x17006879	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1146	0x1700687A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1147	0x1700687B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1148	0x1700687C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1149	0x1700687D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1150	0x1700687E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1151	0x1700687F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1152	0x17006880	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1153	0x17006881	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1154	0x17006882	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1155	0x17006883	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1156	0x17006884	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1157	0x17006885	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1158	0x17006886	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1159	0x17006887	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1160	0x17006888	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1161	0x17006889	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1162	0x1700688A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1163	0x1700688B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1164	0x1700688C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1165	0x1700688D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1166	0x1700688E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1167	0x1700688F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1168	0x17006890	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1169	0x17006891	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1170	0x17006892	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1171	0x17006893	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1172	0x17006894	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1173	0x17006895	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1174	0x17006896	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1175	0x17006897	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1176	0x17006898	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1177	0x17006899	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1178	0x1700689A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1179	0x1700689B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1180	0x1700689C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1181	0x1700689D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1182	0x1700689E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1183	0x1700689F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1184	0x170068A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1185	0x170068A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1186	0x170068A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1187	0x170068A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1188	0x170068A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1189	0x170068A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1190	0x170068A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1191	0x170068A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1192	0x170068A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1193	0x170068A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1194	0x170068AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1195	0x170068AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1196	0x170068AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1197	0x170068AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1198	0x170068AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1199	0x170068AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1200	0x170068B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1201	0x170068B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1202	0x170068B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1203	0x170068B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1204	0x170068B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1205	0x170068B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1206	0x170068B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1207	0x170068B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1208	0x170068B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1209	0x170068B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1210	0x170068BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1211	0x170068BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1212	0x170068BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1213	0x170068BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1214	0x170068BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1215	0x170068BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1216	0x170068C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1217	0x170068C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1218	0x170068C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1219	0x170068C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1220	0x170068C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1221	0x170068C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1222	0x170068C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1223	0x170068C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1224	0x170068C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1225	0x170068C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1226	0x170068CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1227	0x170068CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1228	0x170068CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1229	0x170068CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1230	0x170068CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1231	0x170068CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1232	0x170068D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1233	0x170068D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1234	0x170068D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1235	0x170068D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1236	0x170068D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1237	0x170068D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1238	0x170068D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1239	0x170068D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1240	0x170068D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1241	0x170068D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1242	0x170068DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1243	0x170068DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1244	0x170068DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1245	0x170068DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1246	0x170068DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1247	0x170068DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1248	0x170068E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1249	0x170068E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1250	0x170068E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1251	0x170068E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1252	0x170068E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1253	0x170068E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1254	0x170068E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1255	0x170068E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1256	0x170068E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1257	0x170068E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1258	0x170068EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1259	0x170068EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1260	0x170068EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1261	0x170068ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1262	0x170068EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1263	0x170068EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1264	0x170068F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1265	0x170068F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1266	0x170068F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1267	0x170068F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1268	0x170068F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1269	0x170068F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1270	0x170068F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1271	0x170068F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1272	0x170068F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1273	0x170068F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1274	0x170068FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1275	0x170068FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1276	0x170068FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1277	0x170068FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1278	0x170068FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1279	0x170068FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1280	0x17006900	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1281	0x17006901	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1282	0x17006902	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1283	0x17006903	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1284	0x17006904	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1285	0x17006905	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1286	0x17006906	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1287	0x17006907	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1288	0x17006908	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1289	0x17006909	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1290	0x1700690A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1291	0x1700690B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1292	0x1700690C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1293	0x1700690D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1294	0x1700690E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1295	0x1700690F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1296	0x17006910	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1297	0x17006911	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1298	0x17006912	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1299	0x17006913	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1300	0x17006914	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1301	0x17006915	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1302	0x17006916	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1303	0x17006917	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1304	0x17006918	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1305	0x17006919	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1306	0x1700691A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1307	0x1700691B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1308	0x1700691C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1309	0x1700691D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1310	0x1700691E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1311	0x1700691F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1312	0x17006920	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1313	0x17006921	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1314	0x17006922	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1315	0x17006923	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1316	0x17006924	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1317	0x17006925	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1318	0x17006926	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1319	0x17006927	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1320	0x17006928	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1321	0x17006929	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1322	0x1700692A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1323	0x1700692B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1324	0x1700692C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1325	0x1700692D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1326	0x1700692E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1327	0x1700692F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1328	0x17006930	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1329	0x17006931	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1330	0x17006932	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1331	0x17006933	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1332	0x17006934	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1333	0x17006935	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1334	0x17006936	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1335	0x17006937	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1336	0x17006938	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1337	0x17006939	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1338	0x1700693A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1339	0x1700693B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1340	0x1700693C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1341	0x1700693D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1342	0x1700693E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1343	0x1700693F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1344	0x17006940	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1345	0x17006941	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1346	0x17006942	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1347	0x17006943	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1348	0x17006944	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1349	0x17006945	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1350	0x17006946	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1351	0x17006947	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1352	0x17006948	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1353	0x17006949	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1354	0x1700694A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1355	0x1700694B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1356	0x1700694C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1357	0x1700694D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1358	0x1700694E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1359	0x1700694F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1360	0x17006950	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1361	0x17006951	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1362	0x17006952	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1363	0x17006953	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1364	0x17006954	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1365	0x17006955	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1366	0x17006956	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1367	0x17006957	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1368	0x17006958	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1369	0x17006959	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1370	0x1700695A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1371	0x1700695B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1372	0x1700695C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1373	0x1700695D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1374	0x1700695E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1375	0x1700695F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1376	0x17006960	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1377	0x17006961	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1378	0x17006962	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1379	0x17006963	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1380	0x17006964	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1381	0x17006965	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1382	0x17006966	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1383	0x17006967	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1384	0x17006968	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1385	0x17006969	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1386	0x1700696A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1387	0x1700696B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1388	0x1700696C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1389	0x1700696D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1390	0x1700696E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1391	0x1700696F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1392	0x17006970	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1393	0x17006971	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1394	0x17006972	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1395	0x17006973	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1396	0x17006974	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1397	0x17006975	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1398	0x17006976	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1399	0x17006977	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1400	0x17006978	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1401	0x17006979	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1402	0x1700697A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1403	0x1700697B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1404	0x1700697C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1405	0x1700697D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1406	0x1700697E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1407	0x1700697F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1408	0x17006980	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1409	0x17006981	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1410	0x17006982	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1411	0x17006983	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1412	0x17006984	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1413	0x17006985	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1414	0x17006986	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1415	0x17006987	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1416	0x17006988	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1417	0x17006989	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1418	0x1700698A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1419	0x1700698B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1420	0x1700698C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1421	0x1700698D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1422	0x1700698E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1423	0x1700698F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1424	0x17006990	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1425	0x17006991	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1426	0x17006992	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1427	0x17006993	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1428	0x17006994	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1429	0x17006995	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1430	0x17006996	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1431	0x17006997	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1432	0x17006998	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1433	0x17006999	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1434	0x1700699A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1435	0x1700699B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1436	0x1700699C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1437	0x1700699D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1438	0x1700699E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1439	0x1700699F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1440	0x170069A0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1441	0x170069A1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1442	0x170069A2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1443	0x170069A3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1444	0x170069A4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1445	0x170069A5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1446	0x170069A6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1447	0x170069A7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1448	0x170069A8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1449	0x170069A9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1450	0x170069AA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1451	0x170069AB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1452	0x170069AC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1453	0x170069AD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1454	0x170069AE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1455	0x170069AF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1456	0x170069B0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1457	0x170069B1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1458	0x170069B2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1459	0x170069B3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1460	0x170069B4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1461	0x170069B5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1462	0x170069B6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1463	0x170069B7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1464	0x170069B8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1465	0x170069B9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1466	0x170069BA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1467	0x170069BB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1468	0x170069BC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1469	0x170069BD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1470	0x170069BE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1471	0x170069BF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1472	0x170069C0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1473	0x170069C1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1474	0x170069C2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1475	0x170069C3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1476	0x170069C4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1477	0x170069C5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1478	0x170069C6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1479	0x170069C7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1480	0x170069C8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1481	0x170069C9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1482	0x170069CA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1483	0x170069CB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1484	0x170069CC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1485	0x170069CD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1486	0x170069CE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1487	0x170069CF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1488	0x170069D0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1489	0x170069D1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1490	0x170069D2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1491	0x170069D3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1492	0x170069D4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1493	0x170069D5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1494	0x170069D6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1495	0x170069D7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1496	0x170069D8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1497	0x170069D9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1498	0x170069DA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1499	0x170069DB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1500	0x170069DC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1501	0x170069DD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1502	0x170069DE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1503	0x170069DF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1504	0x170069E0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1505	0x170069E1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1506	0x170069E2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1507	0x170069E3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1508	0x170069E4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1509	0x170069E5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1510	0x170069E6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1511	0x170069E7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1512	0x170069E8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1513	0x170069E9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1514	0x170069EA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1515	0x170069EB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1516	0x170069EC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1517	0x170069ED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1518	0x170069EE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1519	0x170069EF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1520	0x170069F0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1521	0x170069F1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1522	0x170069F2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1523	0x170069F3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1524	0x170069F4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1525	0x170069F5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1526	0x170069F6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1527	0x170069F7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1528	0x170069F8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1529	0x170069F9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1530	0x170069FA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1531	0x170069FB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1532	0x170069FC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1533	0x170069FD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1534	0x170069FE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1535	0x170069FF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1536	0x17006A00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1537	0x17006A01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1538	0x17006A02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1539	0x17006A03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1540	0x17006A04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1541	0x17006A05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1542	0x17006A06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1543	0x17006A07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1544	0x17006A08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1545	0x17006A09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1546	0x17006A0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1547	0x17006A0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1548	0x17006A0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1549	0x17006A0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1550	0x17006A0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1551	0x17006A0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1552	0x17006A10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1553	0x17006A11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1554	0x17006A12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1555	0x17006A13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1556	0x17006A14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1557	0x17006A15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1558	0x17006A16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1559	0x17006A17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1560	0x17006A18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1561	0x17006A19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1562	0x17006A1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1563	0x17006A1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1564	0x17006A1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1565	0x17006A1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1566	0x17006A1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1567	0x17006A1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1568	0x17006A20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1569	0x17006A21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1570	0x17006A22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1571	0x17006A23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1572	0x17006A24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1573	0x17006A25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1574	0x17006A26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1575	0x17006A27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1576	0x17006A28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1577	0x17006A29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1578	0x17006A2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1579	0x17006A2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1580	0x17006A2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1581	0x17006A2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1582	0x17006A2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1583	0x17006A2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1584	0x17006A30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1585	0x17006A31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1586	0x17006A32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1587	0x17006A33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1588	0x17006A34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1589	0x17006A35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1590	0x17006A36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1591	0x17006A37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1592	0x17006A38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1593	0x17006A39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1594	0x17006A3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1595	0x17006A3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1596	0x17006A3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1597	0x17006A3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1598	0x17006A3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1599	0x17006A3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1600	0x17006A40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1601	0x17006A41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1602	0x17006A42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1603	0x17006A43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1604	0x17006A44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1605	0x17006A45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1606	0x17006A46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1607	0x17006A47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1608	0x17006A48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1609	0x17006A49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1610	0x17006A4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1611	0x17006A4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1612	0x17006A4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1613	0x17006A4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1614	0x17006A4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1615	0x17006A4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1616	0x17006A50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1617	0x17006A51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1618	0x17006A52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1619	0x17006A53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1620	0x17006A54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1621	0x17006A55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1622	0x17006A56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1623	0x17006A57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1624	0x17006A58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1625	0x17006A59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1626	0x17006A5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1627	0x17006A5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1628	0x17006A5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1629	0x17006A5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1630	0x17006A5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1631	0x17006A5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1632	0x17006A60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1633	0x17006A61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1634	0x17006A62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1635	0x17006A63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1636	0x17006A64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1637	0x17006A65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1638	0x17006A66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1639	0x17006A67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1640	0x17006A68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1641	0x17006A69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1642	0x17006A6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1643	0x17006A6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1644	0x17006A6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1645	0x17006A6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1646	0x17006A6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1647	0x17006A6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1648	0x17006A70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1649	0x17006A71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1650	0x17006A72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1651	0x17006A73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1652	0x17006A74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1653	0x17006A75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1654	0x17006A76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1655	0x17006A77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1656	0x17006A78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1657	0x17006A79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1658	0x17006A7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1659	0x17006A7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1660	0x17006A7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1661	0x17006A7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1662	0x17006A7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1663	0x17006A7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1664	0x17006A80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1665	0x17006A81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1666	0x17006A82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1667	0x17006A83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1668	0x17006A84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1669	0x17006A85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1670	0x17006A86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1671	0x17006A87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1672	0x17006A88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1673	0x17006A89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1674	0x17006A8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1675	0x17006A8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1676	0x17006A8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1677	0x17006A8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1678	0x17006A8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1679	0x17006A8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1680	0x17006A90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1681	0x17006A91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1682	0x17006A92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1683	0x17006A93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1684	0x17006A94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1685	0x17006A95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1686	0x17006A96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1687	0x17006A97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1688	0x17006A98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1689	0x17006A99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1690	0x17006A9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1691	0x17006A9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1692	0x17006A9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1693	0x17006A9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1694	0x17006A9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1695	0x17006A9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1696	0x17006AA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1697	0x17006AA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1698	0x17006AA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1699	0x17006AA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1700	0x17006AA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1701	0x17006AA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1702	0x17006AA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1703	0x17006AA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1704	0x17006AA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1705	0x17006AA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1706	0x17006AAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1707	0x17006AAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1708	0x17006AAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1709	0x17006AAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1710	0x17006AAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1711	0x17006AAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1712	0x17006AB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1713	0x17006AB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1714	0x17006AB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1715	0x17006AB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1716	0x17006AB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1717	0x17006AB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1718	0x17006AB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1719	0x17006AB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1720	0x17006AB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1721	0x17006AB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1722	0x17006ABA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1723	0x17006ABB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1724	0x17006ABC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1725	0x17006ABD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1726	0x17006ABE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1727	0x17006ABF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1728	0x17006AC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1729	0x17006AC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1730	0x17006AC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1731	0x17006AC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1732	0x17006AC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1733	0x17006AC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1734	0x17006AC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1735	0x17006AC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1736	0x17006AC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1737	0x17006AC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1738	0x17006ACA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1739	0x17006ACB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1740	0x17006ACC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1741	0x17006ACD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1742	0x17006ACE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1743	0x17006ACF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1744	0x17006AD0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1745	0x17006AD1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1746	0x17006AD2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1747	0x17006AD3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1748	0x17006AD4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1749	0x17006AD5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1750	0x17006AD6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1751	0x17006AD7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1752	0x17006AD8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1753	0x17006AD9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1754	0x17006ADA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1755	0x17006ADB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1756	0x17006ADC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1757	0x17006ADD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1758	0x17006ADE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1759	0x17006ADF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1760	0x17006AE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1761	0x17006AE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1762	0x17006AE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1763	0x17006AE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1764	0x17006AE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1765	0x17006AE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1766	0x17006AE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1767	0x17006AE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1768	0x17006AE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1769	0x17006AE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1770	0x17006AEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1771	0x17006AEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1772	0x17006AEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1773	0x17006AED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1774	0x17006AEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1775	0x17006AEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1776	0x17006AF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1777	0x17006AF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1778	0x17006AF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1779	0x17006AF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1780	0x17006AF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1781	0x17006AF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1782	0x17006AF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1783	0x17006AF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1784	0x17006AF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1785	0x17006AF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1786	0x17006AFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1787	0x17006AFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1788	0x17006AFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1789	0x17006AFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1790	0x17006AFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1791	0x17006AFF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1792	0x17006B00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1793	0x17006B01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1794	0x17006B02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1795	0x17006B03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1796	0x17006B04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1797	0x17006B05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1798	0x17006B06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1799	0x17006B07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1800	0x17006B08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1801	0x17006B09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1802	0x17006B0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1803	0x17006B0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1804	0x17006B0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1805	0x17006B0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1806	0x17006B0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1807	0x17006B0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1808	0x17006B10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1809	0x17006B11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1810	0x17006B12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1811	0x17006B13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1812	0x17006B14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1813	0x17006B15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1814	0x17006B16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1815	0x17006B17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1816	0x17006B18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1817	0x17006B19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1818	0x17006B1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1819	0x17006B1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1820	0x17006B1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1821	0x17006B1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1822	0x17006B1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1823	0x17006B1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1824	0x17006B20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1825	0x17006B21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1826	0x17006B22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1827	0x17006B23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1828	0x17006B24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1829	0x17006B25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1830	0x17006B26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1831	0x17006B27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1832	0x17006B28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1833	0x17006B29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1834	0x17006B2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1835	0x17006B2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1836	0x17006B2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1837	0x17006B2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1838	0x17006B2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1839	0x17006B2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1840	0x17006B30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1841	0x17006B31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1842	0x17006B32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1843	0x17006B33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1844	0x17006B34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1845	0x17006B35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1846	0x17006B36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1847	0x17006B37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1848	0x17006B38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1849	0x17006B39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1850	0x17006B3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1851	0x17006B3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1852	0x17006B3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1853	0x17006B3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1854	0x17006B3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1855	0x17006B3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1856	0x17006B40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1857	0x17006B41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1858	0x17006B42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1859	0x17006B43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1860	0x17006B44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1861	0x17006B45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1862	0x17006B46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1863	0x17006B47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1864	0x17006B48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1865	0x17006B49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1866	0x17006B4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1867	0x17006B4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1868	0x17006B4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1869	0x17006B4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1870	0x17006B4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1871	0x17006B4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1872	0x17006B50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1873	0x17006B51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1874	0x17006B52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1875	0x17006B53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1876	0x17006B54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1877	0x17006B55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1878	0x17006B56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1879	0x17006B57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1880	0x17006B58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1881	0x17006B59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1882	0x17006B5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1883	0x17006B5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1884	0x17006B5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1885	0x17006B5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1886	0x17006B5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1887	0x17006B5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1888	0x17006B60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1889	0x17006B61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1890	0x17006B62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1891	0x17006B63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1892	0x17006B64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1893	0x17006B65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1894	0x17006B66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1895	0x17006B67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1896	0x17006B68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1897	0x17006B69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1898	0x17006B6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1899	0x17006B6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1900	0x17006B6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1901	0x17006B6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1902	0x17006B6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1903	0x17006B6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1904	0x17006B70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1905	0x17006B71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1906	0x17006B72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1907	0x17006B73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1908	0x17006B74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1909	0x17006B75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1910	0x17006B76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1911	0x17006B77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1912	0x17006B78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1913	0x17006B79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1914	0x17006B7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1915	0x17006B7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1916	0x17006B7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1917	0x17006B7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1918	0x17006B7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1919	0x17006B7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1920	0x17006B80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1921	0x17006B81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1922	0x17006B82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1923	0x17006B83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1924	0x17006B84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1925	0x17006B85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1926	0x17006B86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1927	0x17006B87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1928	0x17006B88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1929	0x17006B89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1930	0x17006B8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1931	0x17006B8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1932	0x17006B8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1933	0x17006B8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1934	0x17006B8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1935	0x17006B8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1936	0x17006B90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1937	0x17006B91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1938	0x17006B92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1939	0x17006B93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1940	0x17006B94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1941	0x17006B95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1942	0x17006B96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1943	0x17006B97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1944	0x17006B98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1945	0x17006B99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1946	0x17006B9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1947	0x17006B9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1948	0x17006B9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1949	0x17006B9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1950	0x17006B9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1951	0x17006B9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1952	0x17006BA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1953	0x17006BA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1954	0x17006BA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1955	0x17006BA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1956	0x17006BA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1957	0x17006BA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1958	0x17006BA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1959	0x17006BA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1960	0x17006BA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1961	0x17006BA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1962	0x17006BAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1963	0x17006BAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1964	0x17006BAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1965	0x17006BAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1966	0x17006BAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1967	0x17006BAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1968	0x17006BB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1969	0x17006BB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1970	0x17006BB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1971	0x17006BB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1972	0x17006BB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1973	0x17006BB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1974	0x17006BB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1975	0x17006BB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1976	0x17006BB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1977	0x17006BB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1978	0x17006BBA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1979	0x17006BBB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1980	0x17006BBC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1981	0x17006BBD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1982	0x17006BBE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1983	0x17006BBF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY1984	0x17006BC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1985	0x17006BC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1986	0x17006BC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1987	0x17006BC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1988	0x17006BC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1989	0x17006BC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1990	0x17006BC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1991	0x17006BC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1992	0x17006BC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1993	0x17006BC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1994	0x17006BCA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1995	0x17006BCB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1996	0x17006BCC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1997	0x17006BCD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1998	0x17006BCE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY1999	0x17006BCF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2000	0x17006BD0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2001	0x17006BD1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2002	0x17006BD2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2003	0x17006BD3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2004	0x17006BD4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2005	0x17006BD5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2006	0x17006BD6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2007	0x17006BD7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2008	0x17006BD8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2009	0x17006BD9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2010	0x17006BDA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2011	0x17006BDB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2012	0x17006BDC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2013	0x17006BDD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2014	0x17006BDE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2015	0x17006BDF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2016	0x17006BE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2017	0x17006BE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2018	0x17006BE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2019	0x17006BE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2020	0x17006BE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2021	0x17006BE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2022	0x17006BE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2023	0x17006BE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2024	0x17006BE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2025	0x17006BE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2026	0x17006BEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2027	0x17006BEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2028	0x17006BEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2029	0x17006BED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2030	0x17006BEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2031	0x17006BEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2032	0x17006BF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2033	0x17006BF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2034	0x17006BF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2035	0x17006BF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2036	0x17006BF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2037	0x17006BF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2038	0x17006BF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2039	0x17006BF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2040	0x17006BF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2041	0x17006BF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2042	0x17006BFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2043	0x17006BFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2044	0x17006BFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2045	0x17006BFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2046	0x17006BFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2047	0x17006BFF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2048	0x17006C00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2049	0x17006C01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2050	0x17006C02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2051	0x17006C03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2052	0x17006C04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2053	0x17006C05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2054	0x17006C06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2055	0x17006C07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2056	0x17006C08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2057	0x17006C09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2058	0x17006C0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2059	0x17006C0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2060	0x17006C0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2061	0x17006C0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2062	0x17006C0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2063	0x17006C0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2064	0x17006C10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2065	0x17006C11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2066	0x17006C12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2067	0x17006C13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2068	0x17006C14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2069	0x17006C15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2070	0x17006C16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2071	0x17006C17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2072	0x17006C18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2073	0x17006C19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2074	0x17006C1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2075	0x17006C1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2076	0x17006C1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2077	0x17006C1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2078	0x17006C1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2079	0x17006C1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2080	0x17006C20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2081	0x17006C21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2082	0x17006C22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2083	0x17006C23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2084	0x17006C24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2085	0x17006C25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2086	0x17006C26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2087	0x17006C27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2088	0x17006C28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2089	0x17006C29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2090	0x17006C2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2091	0x17006C2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2092	0x17006C2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2093	0x17006C2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2094	0x17006C2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2095	0x17006C2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2096	0x17006C30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2097	0x17006C31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2098	0x17006C32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2099	0x17006C33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2100	0x17006C34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2101	0x17006C35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2102	0x17006C36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2103	0x17006C37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2104	0x17006C38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2105	0x17006C39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2106	0x17006C3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2107	0x17006C3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2108	0x17006C3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2109	0x17006C3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2110	0x17006C3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2111	0x17006C3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2112	0x17006C40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2113	0x17006C41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2114	0x17006C42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2115	0x17006C43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2116	0x17006C44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2117	0x17006C45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2118	0x17006C46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2119	0x17006C47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2120	0x17006C48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2121	0x17006C49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2122	0x17006C4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2123	0x17006C4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2124	0x17006C4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2125	0x17006C4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2126	0x17006C4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2127	0x17006C4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2128	0x17006C50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2129	0x17006C51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2130	0x17006C52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2131	0x17006C53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2132	0x17006C54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2133	0x17006C55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2134	0x17006C56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2135	0x17006C57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2136	0x17006C58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2137	0x17006C59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2138	0x17006C5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2139	0x17006C5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2140	0x17006C5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2141	0x17006C5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2142	0x17006C5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2143	0x17006C5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2144	0x17006C60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2145	0x17006C61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2146	0x17006C62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2147	0x17006C63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2148	0x17006C64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2149	0x17006C65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2150	0x17006C66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2151	0x17006C67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2152	0x17006C68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2153	0x17006C69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2154	0x17006C6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2155	0x17006C6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2156	0x17006C6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2157	0x17006C6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2158	0x17006C6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2159	0x17006C6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2160	0x17006C70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2161	0x17006C71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2162	0x17006C72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2163	0x17006C73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2164	0x17006C74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2165	0x17006C75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2166	0x17006C76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2167	0x17006C77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2168	0x17006C78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2169	0x17006C79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2170	0x17006C7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2171	0x17006C7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2172	0x17006C7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2173	0x17006C7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2174	0x17006C7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2175	0x17006C7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2176	0x17006C80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2177	0x17006C81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2178	0x17006C82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2179	0x17006C83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2180	0x17006C84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2181	0x17006C85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2182	0x17006C86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2183	0x17006C87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2184	0x17006C88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2185	0x17006C89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2186	0x17006C8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2187	0x17006C8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2188	0x17006C8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2189	0x17006C8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2190	0x17006C8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2191	0x17006C8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2192	0x17006C90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2193	0x17006C91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2194	0x17006C92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2195	0x17006C93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2196	0x17006C94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2197	0x17006C95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2198	0x17006C96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2199	0x17006C97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2200	0x17006C98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2201	0x17006C99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2202	0x17006C9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2203	0x17006C9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2204	0x17006C9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2205	0x17006C9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2206	0x17006C9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2207	0x17006C9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2208	0x17006CA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2209	0x17006CA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2210	0x17006CA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2211	0x17006CA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2212	0x17006CA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2213	0x17006CA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2214	0x17006CA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2215	0x17006CA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2216	0x17006CA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2217	0x17006CA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2218	0x17006CAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2219	0x17006CAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2220	0x17006CAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2221	0x17006CAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2222	0x17006CAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2223	0x17006CAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2224	0x17006CB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2225	0x17006CB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2226	0x17006CB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2227	0x17006CB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2228	0x17006CB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2229	0x17006CB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2230	0x17006CB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2231	0x17006CB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2232	0x17006CB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2233	0x17006CB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2234	0x17006CBA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2235	0x17006CBB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2236	0x17006CBC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2237	0x17006CBD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2238	0x17006CBE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2239	0x17006CBF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2240	0x17006CC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2241	0x17006CC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2242	0x17006CC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2243	0x17006CC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2244	0x17006CC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2245	0x17006CC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2246	0x17006CC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2247	0x17006CC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2248	0x17006CC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2249	0x17006CC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2250	0x17006CCA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2251	0x17006CCB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2252	0x17006CCC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2253	0x17006CCD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2254	0x17006CCE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2255	0x17006CCF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2256	0x17006CD0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2257	0x17006CD1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2258	0x17006CD2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2259	0x17006CD3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2260	0x17006CD4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2261	0x17006CD5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2262	0x17006CD6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2263	0x17006CD7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2264	0x17006CD8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2265	0x17006CD9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2266	0x17006CDA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2267	0x17006CDB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2268	0x17006CDC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2269	0x17006CDD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2270	0x17006CDE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2271	0x17006CDF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2272	0x17006CE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2273	0x17006CE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2274	0x17006CE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2275	0x17006CE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2276	0x17006CE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2277	0x17006CE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2278	0x17006CE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2279	0x17006CE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2280	0x17006CE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2281	0x17006CE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2282	0x17006CEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2283	0x17006CEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2284	0x17006CEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2285	0x17006CED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2286	0x17006CEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2287	0x17006CEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2288	0x17006CF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2289	0x17006CF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2290	0x17006CF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2291	0x17006CF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2292	0x17006CF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2293	0x17006CF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2294	0x17006CF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2295	0x17006CF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2296	0x17006CF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2297	0x17006CF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2298	0x17006CFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2299	0x17006CFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2300	0x17006CFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2301	0x17006CFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2302	0x17006CFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2303	0x17006CFF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2304	0x17006D00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2305	0x17006D01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2306	0x17006D02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2307	0x17006D03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2308	0x17006D04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2309	0x17006D05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2310	0x17006D06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2311	0x17006D07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2312	0x17006D08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2313	0x17006D09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2314	0x17006D0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2315	0x17006D0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2316	0x17006D0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2317	0x17006D0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2318	0x17006D0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2319	0x17006D0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2320	0x17006D10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2321	0x17006D11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2322	0x17006D12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2323	0x17006D13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2324	0x17006D14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2325	0x17006D15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2326	0x17006D16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2327	0x17006D17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2328	0x17006D18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2329	0x17006D19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2330	0x17006D1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2331	0x17006D1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2332	0x17006D1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2333	0x17006D1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2334	0x17006D1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2335	0x17006D1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2336	0x17006D20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2337	0x17006D21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2338	0x17006D22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2339	0x17006D23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2340	0x17006D24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2341	0x17006D25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2342	0x17006D26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2343	0x17006D27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2344	0x17006D28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2345	0x17006D29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2346	0x17006D2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2347	0x17006D2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2348	0x17006D2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2349	0x17006D2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2350	0x17006D2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2351	0x17006D2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2352	0x17006D30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2353	0x17006D31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2354	0x17006D32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2355	0x17006D33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2356	0x17006D34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2357	0x17006D35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2358	0x17006D36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2359	0x17006D37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2360	0x17006D38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2361	0x17006D39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2362	0x17006D3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2363	0x17006D3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2364	0x17006D3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2365	0x17006D3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2366	0x17006D3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2367	0x17006D3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2368	0x17006D40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2369	0x17006D41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2370	0x17006D42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2371	0x17006D43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2372	0x17006D44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2373	0x17006D45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2374	0x17006D46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2375	0x17006D47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2376	0x17006D48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2377	0x17006D49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2378	0x17006D4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2379	0x17006D4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2380	0x17006D4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2381	0x17006D4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2382	0x17006D4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2383	0x17006D4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2384	0x17006D50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2385	0x17006D51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2386	0x17006D52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2387	0x17006D53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2388	0x17006D54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2389	0x17006D55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2390	0x17006D56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2391	0x17006D57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2392	0x17006D58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2393	0x17006D59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2394	0x17006D5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2395	0x17006D5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2396	0x17006D5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2397	0x17006D5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2398	0x17006D5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2399	0x17006D5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2400	0x17006D60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2401	0x17006D61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2402	0x17006D62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2403	0x17006D63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2404	0x17006D64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2405	0x17006D65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2406	0x17006D66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2407	0x17006D67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2408	0x17006D68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2409	0x17006D69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2410	0x17006D6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2411	0x17006D6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2412	0x17006D6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2413	0x17006D6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2414	0x17006D6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2415	0x17006D6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2416	0x17006D70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2417	0x17006D71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2418	0x17006D72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2419	0x17006D73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2420	0x17006D74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2421	0x17006D75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2422	0x17006D76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2423	0x17006D77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2424	0x17006D78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2425	0x17006D79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2426	0x17006D7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2427	0x17006D7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2428	0x17006D7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2429	0x17006D7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2430	0x17006D7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2431	0x17006D7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2432	0x17006D80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2433	0x17006D81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2434	0x17006D82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2435	0x17006D83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2436	0x17006D84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2437	0x17006D85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2438	0x17006D86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2439	0x17006D87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2440	0x17006D88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2441	0x17006D89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2442	0x17006D8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2443	0x17006D8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2444	0x17006D8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2445	0x17006D8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2446	0x17006D8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2447	0x17006D8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2448	0x17006D90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2449	0x17006D91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2450	0x17006D92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2451	0x17006D93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2452	0x17006D94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2453	0x17006D95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2454	0x17006D96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2455	0x17006D97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2456	0x17006D98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2457	0x17006D99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2458	0x17006D9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2459	0x17006D9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2460	0x17006D9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2461	0x17006D9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2462	0x17006D9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2463	0x17006D9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2464	0x17006DA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2465	0x17006DA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2466	0x17006DA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2467	0x17006DA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2468	0x17006DA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2469	0x17006DA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2470	0x17006DA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2471	0x17006DA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2472	0x17006DA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2473	0x17006DA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2474	0x17006DAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2475	0x17006DAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2476	0x17006DAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2477	0x17006DAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2478	0x17006DAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2479	0x17006DAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2480	0x17006DB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2481	0x17006DB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2482	0x17006DB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2483	0x17006DB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2484	0x17006DB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2485	0x17006DB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2486	0x17006DB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2487	0x17006DB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2488	0x17006DB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2489	0x17006DB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2490	0x17006DBA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2491	0x17006DBB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2492	0x17006DBC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2493	0x17006DBD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2494	0x17006DBE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2495	0x17006DBF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2496	0x17006DC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2497	0x17006DC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2498	0x17006DC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2499	0x17006DC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2500	0x17006DC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2501	0x17006DC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2502	0x17006DC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2503	0x17006DC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2504	0x17006DC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2505	0x17006DC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2506	0x17006DCA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2507	0x17006DCB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2508	0x17006DCC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2509	0x17006DCD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2510	0x17006DCE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2511	0x17006DCF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2512	0x17006DD0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2513	0x17006DD1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2514	0x17006DD2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2515	0x17006DD3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2516	0x17006DD4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2517	0x17006DD5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2518	0x17006DD6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2519	0x17006DD7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2520	0x17006DD8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2521	0x17006DD9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2522	0x17006DDA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2523	0x17006ddb	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2524	0x17006DDC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2525	0x17006DDD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2526	0x17006DDE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2527	0x17006DDF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2528	0x17006DE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2529	0x17006DE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2530	0x17006DE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2531	0x17006DE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2532	0x17006DE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2533	0x17006DE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2534	0x17006DE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2535	0x17006DE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2536	0x17006DE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2537	0x17006DE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2538	0x17006DEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2539	0x17006DEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2540	0x17006DEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2541	0x17006DED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2542	0x17006DEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2543	0x17006DEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2544	0x17006DF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2545	0x17006DF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2546	0x17006DF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2547	0x17006DF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2548	0x17006DF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2549	0x17006DF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2550	0x17006DF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2551	0x17006DF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2552	0x17006DF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2553	0x17006DF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2554	0x17006DFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2555	0x17006DFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2556	0x17006DFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2557	0x17006DFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2558	0x17006DFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2559	0x17006DFF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2560	0x17006E00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2561	0x17006E01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2562	0x17006E02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2563	0x17006E03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2564	0x17006E04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2565	0x17006E05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2566	0x17006E06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2567	0x17006E07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2568	0x17006E08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2569	0x17006E09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2570	0x17006E0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2571	0x17006E0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2572	0x17006E0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2573	0x17006E0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2574	0x17006E0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2575	0x17006E0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2576	0x17006E10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2577	0x17006E11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2578	0x17006E12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2579	0x17006E13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2580	0x17006E14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2581	0x17006E15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2582	0x17006E16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2583	0x17006E17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2584	0x17006E18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2585	0x17006E19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2586	0x17006E1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2587	0x17006E1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2588	0x17006E1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2589	0x17006E1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2590	0x17006E1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2591	0x17006E1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2592	0x17006E20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2593	0x17006E21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2594	0x17006E22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2595	0x17006E23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2596	0x17006E24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2597	0x17006E25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2598	0x17006E26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2599	0x17006E27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2600	0x17006E28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2601	0x17006E29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2602	0x17006E2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2603	0x17006E2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2604	0x17006E2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2605	0x17006E2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2606	0x17006E2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2607	0x17006E2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2608	0x17006E30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2609	0x17006E31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2610	0x17006E32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2611	0x17006E33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2612	0x17006E34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2613	0x17006E35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2614	0x17006E36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2615	0x17006E37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2616	0x17006E38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2617	0x17006E39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2618	0x17006E3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2619	0x17006E3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2620	0x17006E3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2621	0x17006E3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2622	0x17006E3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2623	0x17006E3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2624	0x17006E40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2625	0x17006E41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2626	0x17006E42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2627	0x17006E43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2628	0x17006E44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2629	0x17006E45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2630	0x17006E46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2631	0x17006E47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2632	0x17006E48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2633	0x17006E49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2634	0x17006E4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2635	0x17006E4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2636	0x17006E4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2637	0x17006E4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2638	0x17006E4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2639	0x17006E4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2640	0x17006E50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2641	0x17006E51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2642	0x17006E52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2643	0x17006E53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2644	0x17006E54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2645	0x17006E55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2646	0x17006E56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2647	0x17006E57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2648	0x17006E58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2649	0x17006E59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2650	0x17006E5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2651	0x17006E5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2652	0x17006E5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2653	0x17006E5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2654	0x17006E5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2655	0x17006E5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2656	0x17006E60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2657	0x17006E61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2658	0x17006E62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2659	0x17006E63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2660	0x17006E64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2661	0x17006E65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2662	0x17006E66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2663	0x17006E67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2664	0x17006E68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2665	0x17006E69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2666	0x17006E6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2667	0x17006E6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2668	0x17006E6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2669	0x17006E6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2670	0x17006E6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2671	0x17006E6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2672	0x17006E70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2673	0x17006E71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2674	0x17006E72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2675	0x17006E73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2676	0x17006E74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2677	0x17006E75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2678	0x17006E76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2679	0x17006E77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2680	0x17006E78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2681	0x17006E79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2682	0x17006E7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2683	0x17006E7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2684	0x17006E7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2685	0x17006E7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2686	0x17006E7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2687	0x17006E7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2688	0x17006E80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2689	0x17006E81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2690	0x17006E82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2691	0x17006E83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2692	0x17006E84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2693	0x17006E85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2694	0x17006E86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2695	0x17006E87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2696	0x17006E88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2697	0x17006E89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2698	0x17006E8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2699	0x17006E8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2700	0x17006E8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2701	0x17006E8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2702	0x17006E8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2703	0x17006E8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2704	0x17006E90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2705	0x17006E91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2706	0x17006E92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2707	0x17006E93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2708	0x17006E94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2709	0x17006E95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2710	0x17006E96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2711	0x17006E97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2712	0x17006E98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2713	0x17006E99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2714	0x17006E9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2715	0x17006E9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2716	0x17006E9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2717	0x17006E9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2718	0x17006E9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2719	0x17006E9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2720	0x17006EA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2721	0x17006EA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2722	0x17006EA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2723	0x17006EA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2724	0x17006EA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2725	0x17006EA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2726	0x17006EA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2727	0x17006EA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2728	0x17006EA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2729	0x17006EA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2730	0x17006EAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2731	0x17006EAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2732	0x17006EAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2733	0x17006EAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2734	0x17006EAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2735	0x17006EAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2736	0x17006EB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2737	0x17006EB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2738	0x17006EB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2739	0x17006EB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2740	0x17006EB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2741	0x17006EB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2742	0x17006EB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2743	0x17006EB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2744	0x17006EB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2745	0x17006EB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2746	0x17006EBA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2747	0x17006EBB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2748	0x17006EBC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2749	0x17006EBD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2750	0x17006EBE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2751	0x17006EBF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2752	0x17006EC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2753	0x17006EC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2754	0x17006EC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2755	0x17006EC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2756	0x17006EC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2757	0x17006EC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2758	0x17006EC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2759	0x17006EC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2760	0x17006EC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2761	0x17006EC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2762	0x17006ECA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2763	0x17006ECB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2764	0x17006ECC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2765	0x17006ECD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2766	0x17006ECE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2767	0x17006ECF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2768	0x17006ED0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2769	0x17006ED1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2770	0x17006ED2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2771	0x17006ED3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2772	0x17006ED4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2773	0x17006ED5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2774	0x17006ED6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2775	0x17006ED7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2776	0x17006ED8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2777	0x17006ED9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2778	0x17006EDA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2779	0x17006EDB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2780	0x17006EDC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2781	0x17006EDD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2782	0x17006EDE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2783	0x17006EDF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2784	0x17006EE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2785	0x17006EE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2786	0x17006EE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2787	0x17006EE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2788	0x17006EE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2789	0x17006EE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2790	0x17006EE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2791	0x17006EE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2792	0x17006EE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2793	0x17006EE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2794	0x17006EEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2795	0x17006EEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2796	0x17006EEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2797	0x17006EED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2798	0x17006EEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2799	0x17006EEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2800	0x17006EF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2801	0x17006EF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2802	0x17006EF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2803	0x17006EF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2804	0x17006EF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2805	0x17006EF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2806	0x17006EF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2807	0x17006EF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2808	0x17006EF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2809	0x17006EF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2810	0x17006EFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2811	0x17006EFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2812	0x17006EFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2813	0x17006EFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2814	0x17006EFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2815	0x17006EFF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2816	0x17006F00	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2817	0x17006F01	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2818	0x17006F02	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2819	0x17006F03	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2820	0x17006F04	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2821	0x17006F05	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2822	0x17006F06	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2823	0x17006F07	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2824	0x17006F08	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2825	0x17006F09	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2826	0x17006F0A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2827	0x17006F0B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2828	0x17006F0C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2829	0x17006F0D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2830	0x17006F0E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2831	0x17006F0F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2832	0x17006F10	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2833	0x17006F11	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2834	0x17006F12	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2835	0x17006F13	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2836	0x17006F14	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2837	0x17006F15	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2838	0x17006F16	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2839	0x17006F17	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2840	0x17006F18	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2841	0x17006F19	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2842	0x17006F1A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2843	0x17006F1B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2844	0x17006F1C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2845	0x17006F1D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2846	0x17006F1E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2847	0x17006F1F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2848	0x17006F20	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2849	0x17006F21	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2850	0x17006F22	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2851	0x17006F23	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2852	0x17006F24	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2853	0x17006F25	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2854	0x17006F26	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2855	0x17006F27	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2856	0x17006F28	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2857	0x17006F29	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2858	0x17006F2A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2859	0x17006F2B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2860	0x17006F2C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2861	0x17006F2D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2862	0x17006F2E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2863	0x17006F2F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2864	0x17006F30	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2865	0x17006F31	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2866	0x17006F32	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2867	0x17006F33	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2868	0x17006F34	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2869	0x17006F35	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2870	0x17006F36	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2871	0x17006F37	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2872	0x17006F38	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2873	0x17006F39	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2874	0x17006F3A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2875	0x17006F3B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2876	0x17006F3C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2877	0x17006F3D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2878	0x17006F3E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2879	0x17006F3F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2880	0x17006F40	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2881	0x17006F41	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2882	0x17006F42	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2883	0x17006F43	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2884	0x17006F44	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2885	0x17006F45	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2886	0x17006F46	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2887	0x17006F47	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2888	0x17006F48	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2889	0x17006F49	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2890	0x17006F4A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2891	0x17006F4B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2892	0x17006F4C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2893	0x17006F4D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2894	0x17006F4E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2895	0x17006F4F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2896	0x17006F50	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2897	0x17006F51	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2898	0x17006F52	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2899	0x17006F53	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2900	0x17006F54	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2901	0x17006F55	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2902	0x17006F56	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2903	0x17006F57	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2904	0x17006F58	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2905	0x17006F59	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2906	0x17006F5A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2907	0x17006F5B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2908	0x17006F5C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2909	0x17006F5D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2910	0x17006F5E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2911	0x17006F5F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2912	0x17006F60	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2913	0x17006F61	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2914	0x17006F62	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2915	0x17006F63	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2916	0x17006F64	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2917	0x17006F65	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2918	0x17006F66	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2919	0x17006F67	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2920	0x17006F68	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2921	0x17006F69	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2922	0x17006F6A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2923	0x17006F6B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2924	0x17006F6C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2925	0x17006F6D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2926	0x17006F6E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2927	0x17006F6F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2928	0x17006F70	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2929	0x17006F71	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2930	0x17006F72	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2931	0x17006F73	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2932	0x17006F74	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2933	0x17006F75	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2934	0x17006F76	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2935	0x17006F77	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2936	0x17006F78	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2937	0x17006F79	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2938	0x17006F7A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2939	0x17006F7B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2940	0x17006F7C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2941	0x17006F7D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2942	0x17006F7E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2943	0x17006F7F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2944	0x17006F80	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2945	0x17006F81	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2946	0x17006F82	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2947	0x17006F83	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2948	0x17006F84	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2949	0x17006F85	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2950	0x17006F86	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2951	0x17006F87	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2952	0x17006F88	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2953	0x17006F89	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2954	0x17006F8A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2955	0x17006F8B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2956	0x17006F8C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2957	0x17006F8D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2958	0x17006F8E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2959	0x17006F8F	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2960	0x17006F90	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2961	0x17006F91	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2962	0x17006F92	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2963	0x17006F93	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2964	0x17006F94	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2965	0x17006F95	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2966	0x17006F96	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2967	0x17006F97	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2968	0x17006F98	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2969	0x17006F99	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2970	0x17006F9A	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2971	0x17006F9B	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2972	0x17006F9C	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2973	0x17006F9D	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2974	0x17006F9E	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2975	0x17006F9F	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY2976	0x17006FA0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2977	0x17006FA1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2978	0x17006FA2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2979	0x17006FA3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2980	0x17006FA4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2981	0x17006FA5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2982	0x17006FA6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2983	0x17006FA7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2984	0x17006FA8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2985	0x17006FA9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2986	0x17006FAA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2987	0x17006FAB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2988	0x17006FAC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2989	0x17006FAD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2990	0x17006FAE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2991	0x17006FAF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2992	0x17006FB0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2993	0x17006FB1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2994	0x17006FB2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2995	0x17006FB3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2996	0x17006FB4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2997	0x17006FB5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2998	0x17006FB6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY2999	0x17006FB7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3000	0x17006FB8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3001	0x17006FB9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3002	0x17006FBA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3003	0x17006FBB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3004	0x17006FBC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3005	0x17006FBD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3006	0x17006FBE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3007	0x17006FBF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY3008	0x17006FC0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3009	0x17006FC1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3010	0x17006FC2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3011	0x17006FC3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3012	0x17006FC4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3013	0x17006FC5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3014	0x17006FC6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3015	0x17006FC7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3016	0x17006FC8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3017	0x17006FC9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3018	0x17006FCA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3019	0x17006FCB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3020	0x17006FCC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3021	0x17006FCD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3022	0x17006FCE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3023	0x17006FCF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3024	0x17006FD0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3025	0x17006FD1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3026	0x17006FD2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3027	0x17006FD3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3028	0x17006FD4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3029	0x17006FD5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3030	0x17006FD6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3031	0x17006FD7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3032	0x17006FD8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3033	0x17006FD9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3034	0x17006FDA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3035	0x17006FDB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3036	0x17006FDC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3037	0x17006FDD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3038	0x17006FDE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3039	0x17006FDF	FULL	Public key for signature verification (max RSA key size 4096)

Register Name	Address	Permission	Description
SFLASH_PUBLIC_KEY3040	0x17006FE0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3041	0x17006FE1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3042	0x17006FE2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3043	0x17006FE3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3044	0x17006FE4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3045	0x17006FE5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3046	0x17006FE6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3047	0x17006FE7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3048	0x17006FE8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3049	0x17006FE9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3050	0x17006FEA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3051	0x17006FEB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3052	0x17006FEC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3053	0x17006FED	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3054	0x17006FEE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3055	0x17006FEF	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3056	0x17006FF0	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3057	0x17006FF1	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3058	0x17006FF2	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3059	0x17006FF3	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3060	0x17006FF4	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3061	0x17006FF5	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3062	0x17006FF6	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3063	0x17006FF7	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3064	0x17006FF8	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3065	0x17006FF9	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3066	0x17006FFA	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3067	0x17006FFB	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3068	0x17006FFC	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3069	0x17006FFD	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3070	0x17006FFE	FULL	Public key for signature verification (max RSA key size 4096)
SFLASH_PUBLIC_KEY3071	0x17006FFF	FULL	Public key for signature verification (max RSA key size 4096)

Technical Reference Manual 2204 002-33817 Rev. **
2021-10-22

Technical Reference Manual 2205 002-33817 Rev. **
2021-10-22

Register Name	Address	Permission	Description
SFLASH_APP_PROT_SETTINGS126	0x170077F8	FULL	Application protection settings (4*128=512 bytes)
SFLASH_APP_PROT_SETTINGS127	0x170077FC	FULL	Application protection settings (4*128=512 bytes)
SFLASH_TOC2_OBJECT_SIZE	0x17007C00	FULL	Object size in bytes for CRC calculation starting from offset 0x00
SFLASH_TOC2_MAGIC_NUMBER	0x17007C04	FULL	Magic number(0x01211220)
SFLASH_TOC2_SMIF_CFG_STRUCT_ADDR	0x17007C08	FULL	Null terminated table of pointers representing the SMIF configuration structure
SFLASH_TOC2_FIRST_USER_APP_ADDR	0x17007C0C	FULL	Address of First User Application Object
SFLASH_TOC2_FIRST_USER_APP_FORMAT	0x17007C10	FULL	Format of First User Application Object. 0 - Basic, 1 - Cypress standard & 2 - Simplified
SFLASH_TOC2_SECOND_USER_APP_ADDR	0x17007C14	FULL	Address of Second User Application Object
SFLASH_TOC2_SECOND_USER_APP_FORMAT	0x17007C18	FULL	Format of Second User Application Object. 0 - Basic, 1 - Cypress standard & 2 - Simplified
SFLASH_TOC2_FIRST_CM4_1_USER_APP_ADDR	0x17007C1C	FULL	Address of First CM4 or CM7 core1 User Application Object
SFLASH_TOC2_SECOND_CM4_1_USER_APP_ADDR	0x17007C20	FULL	Address of Second CM4 or CM7 core1 User Application Object
SFLASH_TOC2_FIRST_CM4_2_USER_APP_ADDR	0x17007C24	FULL	Address of First CM4 or CM7 core2 User Application Object
SFLASH_TOC2_SECOND_CM4_2_USER_APP_ADDR	0x17007C28	FULL	Address of Second CM4 or CM7 core2 User Application Object
SFLASH_TOC2_SECURITY_UPDATES_MARKER	0x17007CFC	FULL	Marker for Security Updates
SFLASH_TOC2_SHASH_OBJECTS	0x17007D00	FULL	Number of additional objects to be verified for SECURE HASH
SFLASH_TOC2_SIGNATURE_VERIF_KEY	0x17007D04	FULL	Address of signature verification key (0 if none).The object is signature specific key. It is the public key in case of RSA
SFLASH_TOC2_APP_PROTECTION_ADDR	0x17007D08	FULL	Address of Application Protection
SFLASH_TOC2_REVISION	0x17007DF4	FULL	Indicates TOC2 Revision. It is not used now.
SFLASH_TOC2_FLAGS	0x17007DF8	FULL	Controls default configuration

26.1 Register Details

26.1.1 SFLASH_SI_REVISION_ID

Description: Indicates Silicon Revision ID of the device
Address: 0x17000001
Offset: 0x1
Retention: Retained
IsDeepSleep: No
Comment: Used to store Silicon Revision ID
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SI_REVISION_ID [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SI_REVISION_ID	RW	RW	X	Silicon Revision ID

26.1.2 SFLASH_SILICON_ID

Description: Indicates Silicon ID of the device
Address: 0x17000002
Offset: 0x2
Retention: Retained
IsDeepSleep: No
Comment: Used to store silicon ID
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ID [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	ID	RW	RW	X	Silicon ID

26.1.3 SFLASH_SFLASH_SVN

Description: SFLASH Subversion
Address: 0x170000A8
Offset: 0xA8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	0	SFLASH Subversion

26.1.4 SFLASH_FB_FLAGS

Description: Flash boot flags
Address: 0x170001FC
Offset: 0x1FC
Retention: Retained
IsDeepSleep: No
Comment: Flash boot flags are used by the flash boot. The default value is 0x0000_0015
Default: 0x15

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		FB_RSA4K_CTL [5:4]		FB_RSA3K_CTL [3:2]		FB_PIN_CTL [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	FB_PIN_CTL	RW	RW	1	Determines toggling a GPIO pin at the start and end of Flash boot 2 = Enable toggling a GPIO pin at the start and end of Flash boot Others = Disable toggling a GPIO pin at the start and end of Flash boot Default value = 1.
2:3	FB_RSA3K_CTL	RW	RW	1	Determines if RSA-3K is supported. 2 = RSA-3K is supported. RSA public key modulo length should be in range 512 to 3072 bit. The field FB_RSA4K_CTL must be set to 0. Others = RSA-3K is not supported. RSA public key modulo length should be in range 512 to 2048 bit. Default value = 1.
4:5	FB_RSA4K_CTL	RW	RW	1	Determines if RSA-4K is supported. 2 = RSA-4K is supported. RSA public key modulo length should be in range 512 to 4096 bit. RSA4K already includes RSA3K option. The field FB_RSA3K_CTL must be set to 0. Others = RSA-4K is not supported. Default value = 1.

26.1.5 SFLASH_EPASS_TEMP_TRIM_TEMP_ROOMSORT

Description: On Chip temperature measured using external currents and external ADC at ROOM
Address: 0x1700064E
Offset: 0x64E
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	On Chip temperature measured using external currents and external ADC at ROOM

26.1.6 SFLASH_EPASS_TEMP_TRIM_DIODE_ROOMSORT

Description: Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at ROOM
Address: 0x17000650
Offset: 0x650
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at ROOM

26.1.7 SFLASH_EPASS_TEMP_TRIM_VBG_ROOMSORT

Description: Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at ROOM
Address: 0x17000652
Offset: 0x652
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at ROOM

26.1.8 SFLASH_EPASS_TEMP_TRIM_TEMP_COLDSORT

Description: On Chip temperature measured using external currents and external ADC at COLD
Address: 0x17000654
Offset: 0x654
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	On Chip temperature measured using external currents and external ADC at COLD

26.1.9 SFLASH_EPASS_TEMP_TRIM_DIODE_COLDSORT

Description: Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at COLD
Address: 0x17000656
Offset: 0x656
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at COLD

26.1.10 SFLASH_EPASS_TEMP_TRIM_VBG_COLDSORT

Description: Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at COLD
Address: 0x17000658
Offset: 0x658
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at COLD

26.1.11 SFLASH_EPASS_TEMP_TRIM_TEMP_HOTCLASS

Description: On Chip temperature measured using external currents and external ADC at HOT
Address: 0x1700065A
Offset: 0x65A
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	On Chip temperature measured using external currents and external ADC at HOT

26.1.12 SFLASH_EPASS_TEMP_TRIM_DIODE_HOTCLASS

Description: Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at HOT
Address: 0x1700065C
Offset: 0x65C
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Temperature sensor diode voltage at HOT

26.1.13 SFLASH_EPASS_TEMP_TRIM_VBG_HOTCLASS

Description: Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at HOT
Address: 0x1700065E
Offset: 0x65E
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=3.3V, Bandgap voltage at HOT

26.1.14 SFLASH_EPASS_TEMP_TRIM_DIODE_ROOMSORT_5V

Description: Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at ROOM
Address: 0x1700066A
Offset: 0x66A
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at ROOM

26.1.15 SFLASH_EPASS_TEMP_TRIM_VBG_ROOMSORT_5V

Description: Temperature sensor calibration data for VDDA=5V, Bandgap voltage at ROOM
Address: 0x1700066C
Offset: 0x66C
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at ROOM

26.1.16 SFLASH_EPASS_TEMP_TRIM_DIODE_COLDSORT_5V

Description: Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at COLD

Address: 0x1700066E

Offset: 0x66E

Retention: Retained

IsDeepSleep: No

Comment: Temperature calibration data for EPASS Temperature sensor

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at COLD

26.1.17 SFLASH_EPASS_TEMP_TRIM_VBG_COLDSORT_5V

Description: Temperature sensor calibration data for VDDA=5V, Bandgap voltage at COLD
Address: 0x17000670
Offset: 0x670
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at COLD

26.1.18 SFLASH_EPASS_TEMP_TRIM_DIODE_HOTCLASS_5V

Description: Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at HOT
Address: 0x17000672
Offset: 0x672
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Temperature sensor diode voltage at HOT

26.1.19 SFLASH_EPASS_TEMP_TRIM_VBG_HOTCLASS_5V

Description: Temperature sensor calibration data for VDDA=5V, Bandgap voltage at HOT
Address: 0x17000674
Offset: 0x674
Retention: Retained
IsDeepSleep: No
Comment: Temperature calibration data for EPASS Temperature sensor
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA16 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA16 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	DATA16	RW	RW	X	Temperature sensor calibration data for VDDA=5V, Bandgap voltage at HOT

26.1.20 SFLASH_SRSS_PWR_OFFSET

Description: SRSS_PWR_OFFSET
Address: 0x17000730
Offset: 0x730
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			PMIC_VADJ_OFFSET [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			REGHC_TRANS_VADJ_OFFSET [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	PMIC_VADJ_OFFSET	RW	RW	X	Die-specific offset for VADJ when using it for feedback to an external PMIC
8:12	REGHC_TRANS_VADJ_OFFSET	RW	RW	X	Die-specific offset for VADJ when using REGHC with external transistor

26.1.21 SFLASH_SRSS_PWR_TRIM_HT_PWRSYS_INTERNAL

Description: Trim settings when the supply is intended to come from the internal regulators
Address: 0x17000734
Offset: 0x734
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x7000010

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			ACT_REG_VTRIM [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				DPSLP_REG_VTRIM [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	ACT_REG_VTRIM	RW	RW	16	Linear Active-Regulator voltage trim.
24:27	DPSLP_REG_VTRIM	RW	RW	7	Linear DeepSleep-Regulator voltage trim.

26.1.22 SFLASH_SRSS_PWR_TRIM_HT_PWRSYS_EXTERNAL

Description: Trim settings for the regulators so they do not interfere with external supply
Address: 0x17000738
Offset: 0x738
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x700000D

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			ACT_REG_VTRIM [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				DPSLP_REG_VTRIM [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	ACT_REG_VTRIM	RW	RW	13	Linear Active-Regulator voltage trim.
24:27	DPSLP_REG_VTRIM	RW	RW	7	Linear DeepSleep-Regulator voltage trim.

26.1.23 SFLASH_USER_FREE_ROW0

Description: USER_FREE_ROW0
Address: 0x17000800
Offset: 0x800
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.24 SFLASH_USER_FREE_ROW1

Description: USER_FREE_ROW1
Address: 0x17000A00
Offset: 0xA00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.25 SFLASH_USER_FREE_ROW2

Description: USER_FREE_ROW2
Address: 0x17000C00
Offset: 0xC00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.26 SFLASH_USER_FREE_ROW3

Description: USER_FREE_ROW3
Address: 0x17000E00
Offset: 0xE00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.27 SFLASH_SFLASH_UPDATE_MARKER

Description: Markers for storing SFLASH programming states
Address: 0x17001800
Offset: 0x1800
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	Marker which indicates SFLASH programming state

26.1.28 SFLASH_FLASH_BOOT_OBJECT_SIZE

Description: Flash Boot - Object Size
Address: 0x17002000
Offset: 0x2000
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.29 SFLASH_FLASH_BOOT_APP_ID

Description: Flash Boot - Application ID/Version
Address: 0x17002004
Offset: 0x2004
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	APP_ID [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	APP_ID [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MINOR_VERSION [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				MAJOR_VERSION [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	APP_ID	RW	RW	X	N/A
16:23	MINOR_VERSION	RW	RW	X	N/A
24:27	MAJOR_VERSION	RW	RW	X	N/A

26.1.30 SFLASH_FLASH_BOOT_VERSION_LOW

Description: Flash Boot - Version Low
Address: 0x17002018
Offset: 0x2018
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.31 SFLASH_FLASH_BOOT_FAMILY_ID

Description: Flash Boot - Family ID
Address: 0x1700201C
Offset: 0x201C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.32 SFLASH_PUBLIC_KEY

Description: Public key for signature verification (max RSA key size 4096)
Address: 0x17006400
Offset: 0x6400
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA	RW	RW	X	N/A

26.1.33 SFLASH_APP_PROT_SETTINGS

Description: Application protection settings (4*128=512 bytes)
Address: 0x17007600
Offset: 0x7600
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.34 SFLASH_TOC2_OBJECT_SIZE

Description: Object size in bytes for CRC calculation starting from offset 0x00
Address: 0x17007C00
Offset: 0x7C00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.35 SFLASH_TOC2_MAGIC_NUMBER

Description: Magic number(0x01211220)
Address: 0x17007C04
Offset: 0x7C04
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.36 SFLASH_TOC2_SMIF_CFG_STRUCT_ADDR

Description: Null terminated table of pointers representing the SMIF configuration structure
Address: 0x17007C08
Offset: 0x7C08
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.37 SFLASH_TOC2_FIRST_USER_APP_ADDR

Description: Address of First User Application Object
Address: 0x17007C0C
Offset: 0x7C0C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.38 SFLASH_TOC2_FIRST_USER_APP_FORMAT

Description: Format of First User Application Object. 0 - Basic, 1 - Cypress standard & 2 - Simplified
Address: 0x17007C10
Offset: 0x7C10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.39 SFLASH_TOC2_SECOND_USER_APP_ADDR

Description: Address of Second User Application Object
Address: 0x17007C14
Offset: 0x7C14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.40 SFLASH_TOC2_SECOND_USER_APP_FORMAT

Description: Format of Second User Application Object. 0 - Basic, 1 - Cypress standard & 2 - Simplified
Address: 0x17007C18
Offset: 0x7C18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.41 SFLASH_TOC2_FIRST_CMX_1_USER_APP_ADDR

Description: Address of First CM4 or CM7 core1 User Application Object
Address: 0x17007C1C
Offset: 0x7C1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	Address of First CM4 or CM7 core1 User Application Object

26.1.42 SFLASH_TOC2_SECOND_CMX_1_USER_APP_ADDR

Description: Address of Second CM4 or CM7 core1 User Application Object
Address: 0x17007C20
Offset: 0x7C20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.43 SFLASH_TOC2_FIRST_CMX_2_USER_APP_ADDR

Description: Address of First CM4 or CM7 core2 User Application Object
Address: 0x17007C24
Offset: 0x7C24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.44 SFLASH_TOC2_SECOND_CMX_2_USER_APP_ADDR

Description: Address of Second CM4 or CM7 core2 User Application Object
Address: 0x17007C28
Offset: 0x7C28
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.45 SFLASH_TOC2_SECURITY_UPDATES_MARKER

Description: Marker for Security Updates
Address: 0x17007CFC
Offset: 0x7CFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	This field is valid in flash boot version 3.1.0.554 and later. When marker is set to 0xFEDEEDDF the following PPU's will be configured during boot: - PERI_MS_PPU_FX_PERI_GR2_GROUP (Fixed PPU) - read only for all PCs; - Programmable PPU#11 configured to allow full access for the following region 0x40201000 - 0x4020100C. The HSM may overwrite the default configuration and reconfigure the PPU. - Programmable PPU#12 configured to allow full access for the CPUSS_ECC_CTL register (0x402013C8). The HSM may overwrite the default configuration and reconfigure the PPU. - Programmable PPU#13 configured to allow full access for the following region 0x40201300 - 0x402013C8. The HSM may overwrite the default configuration and reconfigure the PPU.

26.1.46 SFLASH_TOC2_SHASH_OBJECTS

Description: Number of additional objects to be verified for SECURE_HASH
Address: 0x17007D00
Offset: 0x7D00
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.47 SFLASH_TOC2_SIGNATURE_VERIF_KEY

Description: Address of signature verification key (0 if none). The object is signature specific key. It is the public key in case of RSA

Address: 0x17007D04

Offset: 0x7D04

Retention: Retained

IsDeepSleep: No

Comment:

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.48 SFLASH_TOC2_APP_PROTECTION_ADDR

Description: Address of Application Protection
Address: 0x17007D08
Offset: 0x7D08
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	N/A

26.1.49 SFLASH_TOC2_REVISION

Description: Indicates TOC2 Revision. It is not used now.
Address: 0x17007DF4
Offset: 0x7DF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA32 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA32 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA32 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA32 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	DATA32	RW	RW	X	Indicate TOC2 Revision Value: 0x0000_0000 and 0xFFFF_FFFF - default.

26.1.50 SFLASH_TOC2_FLAGS

Description: Controls default configuration
Address: 0x17007DF8
Offset: 0x7DF8
Retention: Retained
IsDeepSleep: No
Comment: If TOC2 is erased (default), Flash boot assumes TOC2_FLAGS = 0x0000_0243
Default: 0x243

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name		SWJ_PINS_CTL [6:5]		LISTEN_WINDOW [4:2]			CLOCK_CONFIG [1:0]	
Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					FB_BOOTLOADER_CTL [10:9]		APP_AUTH_CTL [8:8]
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	CLOCK_CONFIG	RW	RW	3	Indicates clock frequency configuration. The clock should stay the same after Flash Boot execution. 0 = 8 MHz, IMO, no FLL 1 = 25 MHz, IMO + FLL 2 = 50 MHz, IMO + FLL 3 = Use ROM boot clocks configuration (default) Note: the default value is 2 for Flash boot version earlier than 554.
2:4	LISTEN_WINDOW	RW	RW	0	Determines the Listen window to allow sufficient time to acquire debug port. When CLOCK_CONFIG is set to 3, these window times are calculated assuming ROM boot clock is at 100MHz. 0 = 20 ms (Default) 1 = 10 ms 2 = 1 ms 3 = 0 ms (No Listen window) 4 = 100 ms
5:6	SWJ_PINS_CTL	RW	RW	2	Determines if SWJ pins are configured in SWJ mode by Flash boot. Note: SWJ pins may be enabled later in the user code. 0 = Do not enable SWJ pins in Flash boot. Listen window is skipped. 1 = Do not enable SWJ pins in Flash boot. Listen window is skipped. 2 = Enable SWJ pins in Flash boot (default). 3 = Do not enable SWJ pins in Flash boot. Listen window is skipped.
7:8	APP_AUTH_CTL	RW	RW	0	Determines if the application image digital signature verification (authentication) is performed: 0 = Authentication is enabled (default). 1 = Authentication is disabled. 2 = Authentication is enabled (recommended). 3 = Authentication is enabled.

Bits	Name	SW	HW	Default or Enum	Description
9:10	FB_BOOTLOADER_CTL	RW	RW	1	Determine if the internal bootloader in Flash boot is disabled: 0 = Internal bootloader is disabled. 1 = Internal bootloader is launched if the other bootloader conditions are met (default). 2 = Internal bootloader is disabled. 3 = Internal bootloader is disabled.

27 SMARTIO

Description	Programmable IO configuration
Base Address	0x40320000
Size	0x10000
Slave Num	MMIO3 - 2

27.1 PRT 12

Register Name	Address	Permission	Description
SMARTIO_PRT12_CTL	0x40320C00	FULL	Control register
SMARTIO_PRT12_SYNC_CTL	0x40320C10	FULL	Synchronization control register
SMARTIO_PRT12_LUT_SEL0	0x40320C20	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL1	0x40320C24	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL2	0x40320C28	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL3	0x40320C2C	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL4	0x40320C30	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL5	0x40320C34	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL6	0x40320C38	FULL	LUT component input selection
SMARTIO_PRT12_LUT_SEL7	0x40320C3C	FULL	LUT component input selection
SMARTIO_PRT12_LUT_CTL0	0x40320C40	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL1	0x40320C44	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL2	0x40320C48	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL3	0x40320C4C	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL4	0x40320C50	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL5	0x40320C54	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL6	0x40320C58	FULL	LUT component control register
SMARTIO_PRT12_LUT_CTL7	0x40320C5C	FULL	LUT component control register
SMARTIO_PRT12_DU_SEL	0x40320CC0	FULL	Data unit component input selection
SMARTIO_PRT12_DU_CTL	0x40320CC4	FULL	Data unit component control register
SMARTIO_PRT12_DATA	0x40320CF0	FULL	Data register

27.2 PRT 13

Register Name	Address	Permission	Description
SMARTIO_PRT13_CTL	0x40320D00	FULL	Control register
SMARTIO_PRT13_SYNC_CTL	0x40320D10	FULL	Synchronization control register
SMARTIO_PRT13_LUT_SEL0	0x40320D20	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL1	0x40320D24	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL2	0x40320D28	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL3	0x40320D2C	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL4	0x40320D30	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL5	0x40320D34	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL6	0x40320D38	FULL	LUT component input selection
SMARTIO_PRT13_LUT_SEL7	0x40320D3C	FULL	LUT component input selection
SMARTIO_PRT13_LUT_CTL0	0x40320D40	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL1	0x40320D44	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL2	0x40320D48	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL3	0x40320D4C	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL4	0x40320D50	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL5	0x40320D54	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL6	0x40320D58	FULL	LUT component control register
SMARTIO_PRT13_LUT_CTL7	0x40320D5C	FULL	LUT component control register
SMARTIO_PRT13_DU_SEL	0x40320DC0	FULL	Data unit component input selection
SMARTIO_PRT13_DU_CTL	0x40320DC4	FULL	Data unit component control register
SMARTIO_PRT13_DATA	0x40320DF0	FULL	Data register

27.3 PRT 14

Register Name	Address	Permission	Description
SMARTIO_PRT14_CTL	0x40320E00	FULL	Control register
SMARTIO_PRT14_SYNC_CTL	0x40320E10	FULL	Synchronization control register
SMARTIO_PRT14_LUT_SEL0	0x40320E20	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL1	0x40320E24	FULL	LUT component input selection

Register Name	Address	Permission	Description
SMARTIO_PRT14_LUT_SEL2	0x40320E28	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL3	0x40320E2C	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL4	0x40320E30	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL5	0x40320E34	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL6	0x40320E38	FULL	LUT component input selection
SMARTIO_PRT14_LUT_SEL7	0x40320E3C	FULL	LUT component input selection
SMARTIO_PRT14_LUT_CTL0	0x40320E40	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL1	0x40320E44	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL2	0x40320E48	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL3	0x40320E4C	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL4	0x40320E50	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL5	0x40320E54	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL6	0x40320E58	FULL	LUT component control register
SMARTIO_PRT14_LUT_CTL7	0x40320E5C	FULL	LUT component control register
SMARTIO_PRT14_DU_SEL	0x40320EC0	FULL	Data unit component input selection
SMARTIO_PRT14_DU_CTL	0x40320EC4	FULL	Data unit component control register
SMARTIO_PRT14_DATA	0x40320EF0	FULL	Data register

27.4 PRT 15

Register Name	Address	Permission	Description
SMARTIO_PRT15_CTL	0x40320F00	FULL	Control register
SMARTIO_PRT15_SYNC_CTL	0x40320F10	FULL	Synchronization control register
SMARTIO_PRT15_LUT_SEL0	0x40320F20	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL1	0x40320F24	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL2	0x40320F28	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL3	0x40320F2C	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL4	0x40320F30	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL5	0x40320F34	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL6	0x40320F38	FULL	LUT component input selection
SMARTIO_PRT15_LUT_SEL7	0x40320F3C	FULL	LUT component input selection
SMARTIO_PRT15_LUT_CTL0	0x40320F40	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL1	0x40320F44	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL2	0x40320F48	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL3	0x40320F4C	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL4	0x40320F50	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL5	0x40320F54	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL6	0x40320F58	FULL	LUT component control register
SMARTIO_PRT15_LUT_CTL7	0x40320F5C	FULL	LUT component control register
SMARTIO_PRT15_DU_SEL	0x40320FC0	FULL	Data unit component input selection
SMARTIO_PRT15_DU_CTL	0x40320FC4	FULL	Data unit component control register
SMARTIO_PRT15_DATA	0x40320FF0	FULL	Data register

27.5 PRT 17

Register Name	Address	Permission	Description
SMARTIO_PRT17_CTL	0x40321100	FULL	Control register
SMARTIO_PRT17_SYNC_CTL	0x40321110	FULL	Synchronization control register
SMARTIO_PRT17_LUT_SEL0	0x40321120	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL1	0x40321124	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL2	0x40321128	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL3	0x4032112C	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL4	0x40321130	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL5	0x40321134	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL6	0x40321138	FULL	LUT component input selection
SMARTIO_PRT17_LUT_SEL7	0x4032113C	FULL	LUT component input selection
SMARTIO_PRT17_LUT_CTL0	0x40321140	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL1	0x40321144	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL2	0x40321148	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL3	0x4032114C	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL4	0x40321150	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL5	0x40321154	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL6	0x40321158	FULL	LUT component control register
SMARTIO_PRT17_LUT_CTL7	0x4032115C	FULL	LUT component control register

Register Name	Address	Permission	Description
SMARTIO_PRT17_DU_SEL	0x403211C0	FULL	Data unit component input selection
SMARTIO_PRT17_DU_CTL	0x403211C4	FULL	Data unit component control register
SMARTIO_PRT17_DATA	0x403211F0	FULL	Data register

27.6 Register Details

27.6.1 PRT

27.6.1.1 SMARTIO_PRT_CTL

Description: Control register
Address: 0x40320000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x2001400

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BYPASS [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			CLOCK_SRC [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:26]					PIPELINE_EN [25:25]	HLD_OVR [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	BYPASS	RW	RW	Undefined	Bypass of the programmable IO, one bit for each IO pin: BYPASS[i] is for IO pin i. When ENABLED is '1', this field is used. When ENABLED is '0', this field is NOT used and SMARTIO fabric is always bypassed. '0': No bypass (programmable SMARTIO fabric is exposed). '1': Bypass (programmable SMARTIO fabric is hidden).

Bits	Name	SW	HW	Default or Enum	Description
8:12	CLOCK_SRC	RW	RW	20	Clock ('clk_fabric') and reset ('rst_fabric_n') source selection: '0': io_data_in[0]/'1'. ... '7': io_data_in[7]/'1'. '8': chip_data[0]/'1'. ... '15': chip_data[7]/'1'. '16': clk_smartio/rst_sys_act_n. Used for both Active functionality synchronous logic on 'clk_smartio'. This selection is intended for synchronous operation on a PCLK specified clock frequency ('clock_smartio_pos_en'). Note that the fabric's clocked elements are frequency aligned, but NOT phase aligned to 'clk_sys'. '17': clk_smartio/rst_sys_dpslp_n. Used for both DeepSleep functionality synchronous logic on 'clk_smartio' (note that 'clk_smartio' is NOT available in DeepSleep and Hibernate power modes). This selection is intended for synchronous operation on a PCLK specified clock frequency ('clock_smartio_pos_en'). Note that the fabric's clocked elements are frequency aligned, but NOT phase aligned to 'clk_sys'. '18': Same as '17'. Note that the M0S8 SMARTIO version used the Hibernate reset for this value, but the MXS40 SMARTIO version does not support Hibernate functionality. '19': clk_if/rst_if_dpslp_n (note that 'clk_if' is available in DeepSleep power mode). This selection is intended for synchronous operation on 'clk_if'. Note that the fabric's clocked elements are frequency aligned, but NOT phase aligned to other 'clk_if' clocked elements. '20'-'30': Clock source is constant '0'. Any of these clock sources should be selected when the IP is disabled to ensure low power consumption. '31': asynchronous mode/'1'. Select this when clockless operation is configured. NOTE: Two positive edges of the selected clock are required for the block to be enabled (to deactivate reset). In asynchronous (clockless) mode clk_sys is used to enable the block, but is not available for clocking.
24	HLD_OVR	RW	RW	Undefined	IO cell hold override functionality. In DeepSleep power mode, the HSIOM holds the IO cell output and output enable signals if Active functionality is connected to the IO pads. This is undesirable if the SMARTIO is supposed to deliver DeepSleep output functionality on these IO pads. This field is used to control the hold override functionality from the SMARTIO: '0': The HSIOM controls the IO cell hold override functionality ('hsiom_hld_ovr'). '1': The SMARTIO controls the IO cel hold override functionality: - In bypass mode (ENABLED is '0' or BYPASS[i] is '1'), the HSIOM control is used. - In NON bypass mode (ENABLED is '1' and BYPASS[i] is '0'), the SMARTIO sets hold override to 'pwr_hld_ovr_hib' to enable SMARTIO functionality in DeepSleep power mode (but disables it in Hibernate or Stop power mode).

Bits	Name	SW	HW	Default or Enum	Description
25	PIPELINE_EN	RW	RW	1	Enable for pipeline register: '0': Disabled (register is bypassed). '1': Enabled.
31	ENABLED	RW	RW	0	Enable for programmable IO. Should only be set to '1' when the programmable IO is completely configured: '0': Disabled (signals are bypassed; behavior as if BYPASS is 0xFF). When disabled, the fabric (data unit and LUTs) reset is activated. If the IP is disabled: - The PIPELINE_EN register field should be set to '1', to ensure low power consumption by preventing combinatorial loops. - The CLOCK_SRC register field should be set to '20'-'30' (clock is constant '0'), to ensure low power consumption. '1': Enabled. Once enabled, it takes 3 'clk_fabric' clock cycles till the fabric reset is de-activated and the fabric becomes fully functional. This ensures that the IO pins' input synchronizer states are flushed when the fabric is fully functional.

27.6.1.2 SMARTIO_PRT_SYNC_CTL

Description: Synchronization control register
Address: 0x40320010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	IO_SYNC_EN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CHIP_SYNC_EN [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	IO_SYNC_EN	RW	RW	Undefined	Synchronization of the IO pin input signals to 'clk_fabric', one bit for each IO pin: IO_SYNC_EN[i] is for IO pin i. '0': No synchronization. '1': Synchronization.
8:15	CHIP_SYNC_EN	RW	RW	Undefined	Synchronization of the chip input signals to 'clk_fabric', one bit for each input: CHIP_SYNC_EN[i] is for input i. '0': No synchronization. '1': Synchronization.

27.6.1.3 SMARTIO_PRT_LUT_SEL

Description: LUT component input selection
Address: 0x40320020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				LUT_TR0_SEL [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				LUT_TR1_SEL [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				LUT_TR2_SEL [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	LUT_TR0_SEL	RW	RW	Undefined	LUT input signal 'tr0_in' source selection: '0': Data unit output. '1': LUT 1 output. '2': LUT 2 output. '3': LUT 3 output. '4': LUT 4 output. '5': LUT 5 output. '6': LUT 6 output. '7': LUT 7 output. '8': chip_data[0] (for LUTs 0, 1, 2, 3); chip_data[4] (for LUTs 4, 5, 6, 7). '9': chip_data[1] (for LUTs 0, 1, 2, 3); chip_data[5] (for LUTs 4, 5, 6, 7). '10': chip_data[2] (for LUTs 0, 1, 2, 3); chip_data[6] (for LUTs 4, 5, 6, 7). '11': chip_data[3] (for LUTs 0, 1, 2, 3); chip_data[7] (for LUTs 4, 5, 6, 7). '12': io_data_in[0] (for LUTs 0, 1, 2, 3); io_data_in[4] (for LUTs 4, 5, 6, 7). '13': io_data_in[1] (for LUTs 0, 1, 2, 3); io_data_in[5] (for LUTs 4, 5, 6, 7). '14': io_data_in[2] (for LUTs 0, 1, 2, 3); io_data_in[6] (for LUTs 4, 5, 6, 7). '15': io_data_in[3] (for LUTs 0, 1, 2, 3); io_data_in[7] (for LUTs 4, 5, 6, 7).

Bits	Name	SW	HW	Default or Enum	Description
8:11	LUT_TR1_SEL	RW	RW	Undefined	LUT input signal 'tr1_in' source selection: '0': LUT 0 output. '1': LUT 1 output. '2': LUT 2 output. '3': LUT 3 output. '4': LUT 4 output. '5': LUT 5 output. '6': LUT 6 output. '7': LUT 7 output. '8': chip_data[0] (for LUTs 0, 1, 2, 3); chip_data[4] (for LUTs 4, 5, 6, 7). '9': chip_data[1] (for LUTs 0, 1, 2, 3); chip_data[5] (for LUTs 4, 5, 6, 7). '10': chip_data[2] (for LUTs 0, 1, 2, 3); chip_data[6] (for LUTs 4, 5, 6, 7). '11': chip_data[3] (for LUTs 0, 1, 2, 3); chip_data[7] (for LUTs 4, 5, 6, 7). '12': io_data_in[0] (for LUTs 0, 1, 2, 3); io_data_in[4] (for LUTs 4, 5, 6, 7). '13': io_data_in[1] (for LUTs 0, 1, 2, 3); io_data_in[5] (for LUTs 4, 5, 6, 7). '14': io_data_in[2] (for LUTs 0, 1, 2, 3); io_data_in[6] (for LUTs 4, 5, 6, 7). '15': io_data_in[3] (for LUTs 0, 1, 2, 3); io_data_in[7] (for LUTs 4, 5, 6, 7).
16:19	LUT_TR2_SEL	RW	RW	Undefined	LUT input signal 'tr2_in' source selection. Encoding is the same as for LUT_TR1_SEL.

27.6.1.4 SMARTIO_PRT_LUT_CTL

Description: LUT component control register
Address: 0x40320040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LUT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						LUT_OPC [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	LUT	RW	RW	Undefined	LUT configuration. Depending on the LUT opcode LUT_OPC, the internal state lut_reg (captured in a flip-flop) and the LUT input signals tr0_in, tr1_in, tr2_in, the LUT configuration is used to determine the LUT output signal and the next sequential state (lut_reg).
8:9	LUT_OPC	RW	RW	Undefined	LUT opcode specifies the LUT operation: '0': Combinatorial output, no feedback. $tr\_out = LUT[\{tr2\_in, tr1\_in, tr0\_in\}]$. '1': Combinatorial output, feedback. $tr\_out = LUT[\{lut\_reg, tr1\_in, tr0\_in\}]$. On clock: $lut\_reg \leq tr\_in2$. '2': Sequential output, no feedback. $temp = LUT[\{tr2\_in, tr1\_in, tr0\_in\}]$. $tr\_out = lut\_reg$. On clock: $lut\_reg \leq temp$. '3': Register with asynchronous set and reset. $tr\_out = lut\_reg$. $enable = (tr2\_in \wedge LUT[4]) \vee LUT[5]$. $set = enable \wedge (tr1\_in \wedge LUT[2]) \wedge LUT[3]$. $clr = enable \wedge (tr0\_in \wedge LUT[0]) \wedge LUT[1]$. Asynchronously (no clock required): $lut\_reg \leq \text{if } (clr) '0' \text{ else if } (set) '1'$

27.6.1.5 SMARTIO_PRT_DU_SEL

Description: Data unit component input selection
Address: 0x403200C0
Offset: 0xC0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				DU_TR0_SEL [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				DU_TR1_SEL [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:20]				DU_TR2_SEL [19:16]			

Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		DU_DATA1_SEL [29:28]		None [27:26]		DU_DATA0_SEL [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	DU_TR0_SEL	RW	RW	Undefined	Data unit input signal 'tr0_in' source selection: '0': Constant '0'. '1': Constant '1'. '2': Data unit output. '10-3': LUT 7 - 0 outputs. Otherwise: Undefined.
8:11	DU_TR1_SEL	RW	RW	Undefined	Data unit input signal 'tr1_in' source selection. Encoding is the same as for DU_TR0_SEL.
16:19	DU_TR2_SEL	RW	RW	Undefined	Data unit input signal 'tr2_in' source selection. Encoding is the same as for DU_TR0_SEL.
24:25	DU_DATA0_SEL	RW	RW	Undefined	Data unit input data 'data0_in' source selection: '0': Constant '0'. '1': chip_data[7:0]. '2': io_data_in[7:0]. '3': DATA.DATA MMIO register field.
28:29	DU_DATA1_SEL	RW	RW	Undefined	Data unit input data 'data1_in' source selection. Encoding is the same as for DU_DATA0_SEL.

27.6.1.6 SMARTIO_PRT_DU_CTL

Description: Data unit component control register
Address: 0x403200C4
Offset: 0xC4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					DU_SIZE [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]					DU_OPC [11:8]		

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	DU_SIZE	RW	RW	Undefined	Size/width of the data unit data operands (in bits) is DU_SIZE+1. E.g., if DU_SIZE is 7, the width is 8 bits.
8:11	DU_OPC	RW	RW	Undefined	Data unit opcode specifies the data unit operation: '1': INCR '2': DECR '3': INCR_WRAP '4': DECR_WRAP '5': INCR_DECR '6': INCR_DECR_WRAP '7': ROR '8': SHR '9': AND_OR '10': SHR_MAJ3 '11': SHR_EQL. Otherwise: Undefined.

27.6.1.7 SMARTIO_PRT_DATA

Description: Data register
Address: 0x403200F0
Offset: 0xF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA	RW	RW	Undefined	Data unit input data source.

28 SMIF

Description	Serial Memory Interface
Base Address	0x40420000
Size	0x10000
Slave Num	MMIO4 - 0

Register Name	Address	Permission	Description
SMIF0_CTL	0x40420000	FULL	Control Note:INT_CLOCK_DL_ENABLED INT_CLOCK_CAPTURE_CYCLE are not available for this register
SMIF0_STATUS	0x40420004	FULL	Status
SMIF0_DELAY_TAP_SEL	0x40420030	FULL	Delay Tap Select Register
SMIF0_TX_CMD_FIFO_STATUS	0x40420044	FULL	Transmitter command FIFO status
SMIF0_TX_CMD_FIFO_WR	0x40420050	FULL	Transmitter command FIFO write
SMIF0_TX_DATA_FIFO_CTL	0x40420080	FULL	Transmitter data FIFO control
SMIF0_TX_DATA_FIFO_STATUS	0x40420084	FULL	Transmitter data FIFO status
SMIF0_TX_DATA_FIFO_WR1	0x40420090	FULL	Transmitter data FIFO write
SMIF0_TX_DATA_FIFO_WR2	0x40420094	FULL	Transmitter data FIFO write
SMIF0_TX_DATA_FIFO_WR4	0x40420098	FULL	Transmitter data FIFO write
SMIF0_TX_DATA_FIFO_WR1ODD	0x4042009C	FULL	Transmitter data FIFO write
SMIF0_RX_DATA_MMIO_FIFO_CTL	0x404200C0	FULL	Receiver data MMIO FIFO control
SMIF0_RX_DATA_MMIO_FIFO_STATUS	0x404200C4	FULL	Receiver data MMIO FIFO status
SMIF0_RX_DATA_FIFO_STATUS	0x404200C8	FULL	Receiver data FIFO status
SMIF0_RX_DATA_MMIO_FIFO_RD1	0x404200D0	FULL	Receiver data MMIO FIFO read
SMIF0_RX_DATA_MMIO_FIFO_RD2	0x404200D4	FULL	Receiver data MMIO FIFO read
SMIF0_RX_DATA_MMIO_FIFO_RD4	0x404200D8	FULL	Receiver data MMIO FIFO read
SMIF0_RX_DATA_MMIO_FIFO_RD1_SILENT	0x404200E0	FULL	Receiver data MMIO FIFO silent read
SMIF0_SLOW_CA_CTL	0x40420100	FULL	Slow cache control
SMIF0_SLOW_CA_CMD	0x40420108	FULL	Slow cache command
SMIF0_CRYPT0_CMD	0x40420200	FULL	Cryptography Command
SMIF0_CRYPT0_INPUT0	0x40420220	FULL	Cryptography input 0
SMIF0_CRYPT0_INPUT1	0x40420224	FULL	Cryptography input 1
SMIF0_CRYPT0_INPUT2	0x40420228	FULL	Cryptography input 2
SMIF0_CRYPT0_INPUT3	0x4042022C	FULL	Cryptography input 3
SMIF0_CRYPT0_KEY0	0x40420240	FULL	Cryptography key 0
SMIF0_CRYPT0_KEY1	0x40420244	FULL	Cryptography key 1
SMIF0_CRYPT0_KEY2	0x40420248	FULL	Cryptography key 2
SMIF0_CRYPT0_KEY3	0x4042024C	FULL	Cryptography key 3
SMIF0_CRYPT0_OUTPUT0	0x40420260	FULL	Cryptography output 0
SMIF0_CRYPT0_OUTPUT1	0x40420264	FULL	Cryptography output 1
SMIF0_CRYPT0_OUTPUT2	0x40420268	FULL	Cryptography output 2
SMIF0_CRYPT0_OUTPUT3	0x4042026C	FULL	Cryptography output 3
SMIF0_INTR	0x404207C0	FULL	Interrupt register Note:DL_FAIL DL_WARNING CRC_ERROR FS_STATUS_ERROR are not available for this register
SMIF0_INTR_SET	0x404207C4	FULL	Interrupt set register Note:DL_FAIL DL_WARNING CRC_ERROR FS_STATUS_ERROR are not available for this register
SMIF0_INTR_MASK	0x404207C8	FULL	Interrupt mask register Note:DL_FAIL DL_WARNING CRC_ERROR FS_STATUS_ERROR are not available for this register
SMIF0_INTR_MASKED	0x404207CC	FULL	Interrupt masked register Note:DL_FAIL DL_WARNING CRC_ERROR FS_STATUS_ERROR are not available for this register

28.1 DEVICE 0

Register Name	Address	Permission	Description
SMIF0_DEVICE0_CTL	0x40420800	FULL	Control
SMIF0_DEVICE0_ADDR	0x40420808	FULL	Device region base address
SMIF0_DEVICE0_MASK	0x4042080C	FULL	Device region mask
SMIF0_DEVICE0_ADDR_CTL	0x40420820	FULL	Address control
SMIF0_DEVICE0_RD_CMD_CTL	0x40420840	FULL	Read command control

Register Name	Address	Permission	Description
SMIF0_DEVICE0_RD_ADDR_CTL	0x40420844	FULL	Read address control
SMIF0_DEVICE0_RD_MODE_CTL	0x40420848	FULL	Read mode control
SMIF0_DEVICE0_RD_DUMMY_CTL	0x4042084C	FULL	Read dummy control
SMIF0_DEVICE0_RD_DATA_CTL	0x40420850	FULL	Read data control
SMIF0_DEVICE0_RD_BOUND_CTL	0x40420858	FULL	Read boundary control
SMIF0_DEVICE0_WR_CMD_CTL	0x40420860	FULL	Write command control
SMIF0_DEVICE0_WR_ADDR_CTL	0x40420864	FULL	Write address control
SMIF0_DEVICE0_WR_MODE_CTL	0x40420868	FULL	Write mode control
SMIF0_DEVICE0_WR_DUMMY_CTL	0x4042086C	FULL	Write dummy control
SMIF0_DEVICE0_WR_DATA_CTL	0x40420870	FULL	Write data control

28.2 DEVICE 1

Register Name	Address	Permission	Description
SMIF0_DEVICE1_CTL	0x40420880	FULL	Control
SMIF0_DEVICE1_ADDR	0x40420888	FULL	Device region base address
SMIF0_DEVICE1_MASK	0x4042088C	FULL	Device region mask
SMIF0_DEVICE1_ADDR_CTL	0x404208A0	FULL	Address control
SMIF0_DEVICE1_RD_CMD_CTL	0x404208C0	FULL	Read command control
SMIF0_DEVICE1_RD_ADDR_CTL	0x404208C4	FULL	Read address control
SMIF0_DEVICE1_RD_MODE_CTL	0x404208C8	FULL	Read mode control
SMIF0_DEVICE1_RD_DUMMY_CTL	0x404208CC	FULL	Read dummy control
SMIF0_DEVICE1_RD_DATA_CTL	0x404208D0	FULL	Read data control
SMIF0_DEVICE1_RD_BOUND_CTL	0x404208D8	FULL	Read boundary control
SMIF0_DEVICE1_WR_CMD_CTL	0x404208E0	FULL	Write command control
SMIF0_DEVICE1_WR_ADDR_CTL	0x404208E4	FULL	Write address control
SMIF0_DEVICE1_WR_MODE_CTL	0x404208E8	FULL	Write mode control
SMIF0_DEVICE1_WR_DUMMY_CTL	0x404208EC	FULL	Write dummy control
SMIF0_DEVICE1_WR_DATA_CTL	0x404208F0	FULL	Write data control

28.3 Register Details

28.3.1 SMIF_CTL

Description:	Control
Address:	0x40420000
Offset:	0x0
Retention:	Retained
IsDeepSleep:	No
Comment:	The register fields should only be changed when the IP is disabled; i.e. CTL.ENABLED is '0'. The only exception to this rule is the CTL.XIP_MODE field, which can be changed when the IP is enabled.
Default:	0x503400

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DELAY_LINE_SEL [7:5]			CLOCK_IF_TX_SEL [4:4]	None [3:1]			XIP_MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	CLOCK_IF_RX_SEL [14:12]			INT_CLOCK_CAPTURE_CYCLE [11:10]		INT_CLOCK_DL_ENABLED [9:9]	DELAY_TAP_ENABLED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	SELECT_HOLD_DELAY [23:22]		SELECT_SETUP_DELAY [21:20]		None [19:19]	DESELECT_DELAY [18:16]		

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	None [30:25]						BLOCK [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	XIP_MODE	RW	RW	0	Mode of operation. Note: this field should only be changed when the IP is disabled or when STATUS.BUSY is '0' and SW should not be executing from the XIP interface or MMIO interface.
	MMIO_MODE			0	'0': MMIO mode. Individual MMIO accesses to TX and RX FIFOs are used to generate a sequence of SPI transfers. This mode of operation allows for large flexibility in terms of the SPI transfers that can be generated.
	XIP_MODE			1	'1': XIP mode. eXecute-In-Place mode: incoming read and write transfers over the AHB-Lite bus infrastructure are automatically translated in SPI transfers to read data from and write data to a device. This mode of operation allow for efficient device read and write operations. This mode is only supported in SPI_MODE.

Bits	Name	SW	HW	Default or Enum	Description
4	CLOCK_IF_TX_SEL	RW	RW	0	Specifies device interface transmitter clock options. '0': SDR. Memory interface clock 'spihb_clk_out' is divided (by 2) interface clock 'clk_if', memory interface data signals are driven by divided (by 2) interface clock 'clk_if' with different phase than 'spihb_clk_out'. Results in driving memory interface data signals at falling 'spihb_clk_out' edge. '1': DDR. Memory interface clock 'spihb_clk_out' is divided (by 2) inverted interface clock 'clk_if_inv', memory interface data signals are driven with interface clock 'clk_if'. Results in driving memory interface data signals 90 degrees before rising and falling 'spihb_clk_out' edge.
5:7	DELAY_LINE_SEL	RW	RW	0	Specifies the delay line used for RX data capturing with - output / feedback clock based capturing (when CLOCK_IF_RX_SEL = [0..3] and DELAY_TAP_ENABLED = 1) - internal clock based capturing (when CLOCK_IF_RX_SEL = [4..5], INT_CLOCK_CAPTURE_PRESENT = 1 and DELAY_TAP_ENABLED = 1) - RWDS based capturing (when CLOCK_IF_RX_SEL = [6..7])
8	DELAY_TAP_ENABLED	RW	RW	0	Delay Line Tap Enable. '0': Disabled. The delay line tap selections specified in registers DELAY_TAP_SEL or INT_CLOCK_DELAY_TAP_SEL0/1 are not used. The read data is directly captured by the RX data FIFO capture clock as specified by CLOCK_IF_RX_SEL and INT_CLOCK_CAPTURE_CYCLE. '1': Enabled. The delay line tap selections specified in registers DELAY_TAP_SEL or INT_CLOCK_DELAY_TAP_SEL0/1 are used. Note that in RWDS based capture scheme (CLOCK_IF_RX_SEL = [6..7]), DELAY_TAP_ENABLED must be set to '1' as the RWDS based capture scheme requires to use the delay line. If the output / feedback clock based capture scheme (CLOCK_IF_RX_SEL = [0..3]) or the RWDS based capture scheme (CLOCK_IF_RX_SEL = [6..7]) is selected then the register DELAY_TAP_SEL is used to select the capture clock. If the internal clock based capture scheme (CLOCK_IF_RX_SEL = [4..5] and INT_CLOCK_CAPTURE_PRESENT = 1) is selected then the registers INT_CLOCK_DELAY_TAP_SEL0/1 are used to select the capture clock per data bit line (read data is captured by the capture logic and afterwards transferred to the RX data FIFO).

Bits	Name	SW	HW	Default or Enum	Description
9	INT_CLOCK_DL_ENABLED	RW	RW	0	Data Learning Enable for internal RX clock based on Data Learning Pattern. Only applies when <code>CLOCK_IF_RX_SEL = [4..5]</code> for selecting the internal clock based capture scheme and when <code>DELAY_TAP_ENABLED = 1</code>. '0': Disabled. The delay line tap selections specified in registers <code>INT_CLOCK_DELAY_TAP_SEL0/1</code> are not modified by HW. '1': Enabled. The delay line tap selections specified in registers <code>INT_CLOCK_DELAY_TAP_SEL0/1</code> are modified by HW based on the data learning pattern. From all capture clock delay line taps producing a match between the expected data learning pattern in register DLP and the captured data learning pattern from the memory device the middle one is selected.
10:11	INT_CLOCK_CAPTURE_CYCLE	RW	RW	1	Specifies the read data capture cycle for internal clocking. Only applies when <code>CLOCK_IF_RX_SEL</code> is set to '4' or '5'. If <code>CLOCK_IF_RX_SEL</code> is not set to '4' or '5' then <code>INT_CLOCK_CAPTURE_CYCLE</code> must be set to '0'. Together with <code>CLOCK_IF_RX_SEL</code> ('4' / '5') and <code>INT_CLOCK_CAPTURE_CYCLE</code> an <code>clk_if</code> edge for read data capturing can be selected (coarse capture delay grid between 0.5 and 3 <code>clk_if</code> cycles). '0': Cycle 0. - If <code>CLOCK_IF_RX_SEL=5</code> the capture time is 0.5 <code>clk_if</code> cycles after the memory device read data driving clock edge. For very short signal delays. - If <code>CLOCK_IF_RX_SEL=4</code> the capture time is 1 <code>clk_if</code> cycles after the memory device read data driving clock edge. For short signal delays. '1': Cycle 1. - If <code>CLOCK_IF_RX_SEL=5</code> the capture time is 1.5 <code>clk_if</code> cycles after the memory device read data driving clock edge. For medium signal delays. - If <code>CLOCK_IF_RX_SEL=4</code> the capture time is 2 <code>clk_if</code> cycle after the memory device read data driving clock edge. For long signal delays. '2': Cycle 2. - If <code>CLOCK_IF_RX_SEL=5</code> the capture time is 2.5 <code>clk_if</code> cycles after the memory device read data driving clock edge. For very long signal delays. - If <code>CLOCK_IF_RX_SEL=4</code> the capture time is 3 <code>clk_if</code> cycles after the memory device read data driving clock edge. For very long signal delays. '3': Reserved. Do not use.

Bits	Name	SW	HW	Default or Enum	Description
12:14	CLOCK_IF_RX_SEL	RW	RW	3	Specifies device interface receiver clock 'clk_if_rx' source. MISO data is captured on the rising edge of 'clk_if_rx' in SDR mode and on both edges of 'clk_if_rx' in DDR mode. '0': 'spi_clk_out' (output clock) for SDR capturing with output clock '1': 'spi_clk_out' (output clock) for DDR or SDR capturing with inverted output clock '2': 'spi_clk_in' (feedback clock) for SDR capturing with feedback clock '3': 'spi_clk_in' (feedback clock) for DDR or SDR capturing with inverted feedback clock '4': 'clk_if_tx' (internal clock) for DDR or SDR capturing with internal clock '5': 'clk_if_tx_inv' (internal clock) for DDR or SDR capturing with inverted internal clock '6': 'sphb_rwds_inv' (RWDS / DQS strobe signal driven by memory device) for DDR capturing with RWDS / DQS in Hyperbus / Octal SPI mode or for SDR capturing with falling RWDS / DQS edge in Octal SPI mode '7': 'sphb_rwds' (RWDS / DQS strobe signal driven by memory device) for SDR capturing with rising RWDS / DQS edge in Octal SPI mode
16:18	DESELECT_DELAY	RW	RW	0	Specifies the minimum duration of SPI deselection ('spi_select_out[]' is high/'1') in between SPI transfers: '0': 1 memory interface clock cycle. '1': 2 memory interface clock cycles. '2': 3 memory interface clock cycles. '3': 4 memory interface clock cycles. '4': 5 memory interface clock cycles. '5': 6 memory interface clock cycles. '6': 7 memory interface clock cycles. '7': 8 memory interface clock cycles. During SPI deselection, 'spi_select_out[]' are '1'/inactive, 'spi_data_out[]' are '1' and 'spi_clk_out' is '0'/inactive.
20:21	SELECT_SETUP_DELAY	RW	RW	1	Specifies the duration between 'spi_select_out[]' becomes low/'0') to 1st 'spi_clk_out' edge: '0': 0 memory interface clock cycles + min. duration (see below). '1': 1 memory interface clock cycle + min. duration (see below). '2': 2 memory interface clock cycles + min. duration (see below). '3': 3 memory interface clock cycles + min. duration (see below). In addition to the number of cycles selected here there is a min. duration of: - 1 memory interface clock cycle (= 2 clk_if cycle) for SDR timing (CLOCK_IF_TX_SEL = 0) - 1/4 memory interface clock cycle (= 1/2 clk_if cycle) for DDR timing (CLOCK_IF_TX_SEL = 1)

Bits	Name	SW	HW	Default or Enum	Description
22:23	SELECT_HOLD_DELAY	RW	RW	1	Specifies the duration between last 'spi_clk_out' edge to 'spi_select_out[]' becomes high/'1'): '0': 0 memory interface clock cycles + min. duration (see below). '1': 1 memory interface clock cycle + min. duration (see below). '2': 2 memory interface clock cycles + min. duration (see below). '3': 3 memory interface clock cycles + min. duration (see below). In addition to the number of cycles selected here there is a min. duration of: - 1/2 memory interface clock cycle (= 1 clk_if cycles) for SDR timing (CLOCK_IF_TX_SEL = 0) - 1/4 memory interface clock cycle (= 1/2 clk_if cycle) for DDR timing (CLOCK_IF_TX_SEL = 1)
24	BLOCK	RW	RW	0	Specifies what happens for MMIO interface read accesses to an empty RX data FIFO or to a full TX format/data FIFO. Note: the FIFOs can only be accessed in MMIO_MODE. This field is not used for test controller accesses.
	BUS_ERROR			0	0': Generate an AHB-Lite bus error. This option is useful when SW decides to use polling on STATUS.TR_BUSY to determine if a interface transfer is no longer busy (transfer is completed). This option adds SW complexity, but limits the number of AHB-Lite wait states (and limits ISR latency).
	WAIT_STATES			1	1': Introduce wait states. This setting potentially locks up the AHB-Lite infrastructure and may increase the CPU interrupt latency. This option is useful when SW performs TX/RX data FIFO accesses immediately after a command is setup using the TX format FIFO. This option has low SW complexity, but may result in a significant number of AHB-Lite wait states (and may increase ISR latency).
31	ENABLED	RW	RW	0	IP enable: '0': Disabled. All non-retention registers are reset to their default value when the IP is disabled. When the IP is disabled, the XIP accesses produce AHB-Lite bus errors. '1': Enabled. Notes: - Before disabling the IP, SW should ensure that the IP is NOT busy (STATUS.BUSY is '0'), otherwise illegal interface transfers may occur. - After CTL.ENABLED is set to 1 it takes up to 20 clk_if cycles until the memory interface registers are released from reset.
	DISABLED			0	N/A
	ENABLED			1	N/A

28.3.2 SMIF_STATUS

Description: Status
Address: 0x40420004
Offset: 0x4
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	BUSY	R	R	0	AHB Cache, AXI interface, cryptography, XIP, device interface or any other logic busy in the IP: '0': not busy '1': busy When BUSY is '0', the IP can be safely disabled without: - the potential loss of transient write data. - the potential risk of aborting an inflight SPI device interface transfer. When BUSY is '0', the mode of operation (XIP_MODE or MMIO_MODE) can be safely changed.

28.3.3 SMIF_DELAY_TAP_SEL

Description: Delay Tap Select Register
Address: 0x40420030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SEL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	SEL	RW	RW	1	Delay line tap selection in output / feedback clock based capture scheme (CLOCK_IF_RX_SEL = [0..3]) and RWDS capture scheme (CLOCK_IF_RX_SEL = [6..7]). This is used to shift the strobe signal into the data eye. Note: DELAY_TAP_SEL must not be changed while STATUS.BUSY=1.

28.3.4 SMIF_TX_CMD_FIFO_STATUS

Description: Transmitter command FIFO status
Address: 0x40420044
Offset: 0x44
Retention: Not Retained
IsDeepSleep: No
Comment: The TX command FIFO has 4 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				USED4 [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	USED4	R	R	0	Number of entries that are used in the TX command FIFO (available in both XIP_MODE and MMIO_MODE). Legal range: [0, 8].

28.3.5 SMIF_TX_CMD_FIFO_WR

Description: Transmitter command FIFO write
Address: 0x40420050
Offset: 0x50
Retention: Not Retained
IsDeepSleep: No
Comment: A read from this register returns '0'. A write to this register in XIP_MODE results in an AHB-Lite bus error. A write to this register in MMIO_MODE writes the top of the FIFO.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA27 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA27 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA27 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:27]					DATA27 [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:26	DATA27	W	W	0	Command data. The higher two bits DATA[26:24] specify the specific command '0'/TX: A SPI transfer always start with a TX command FIFO entry of the 'TX' format. - DATA[23:20] specifies which of the four devices are selected. DATA[23:20] are directly mapped to 'spi_select_out[3:0]'. Two devices can be selected at the same time in dual-quad mode. - '0': device deselected - '1': device selected - DATA[19] specifies whether this is the last TX Byte; i.e. whether the 'spi_select_out[3:0]' IO output signals are de-activated after the transfer. - '0': not the last TX byte - '1': the last TX byte - DATA[18] specifies the mode of transfer rate: - '0': SDR mode - '1': DDR mode - DATA[17:16] specifies the width of the data transfer: - '0': 1 bit/cycle (single data transfer). - '1': 2 bits/cycle (dual data transfer). - '2': 4 bits/cycle (quad data transfer). - '3': 8 bits/cycle (octal data transfer). - DATA[15:8] specifies the second transmitted Byte. This is only used (and must be specified) for octal data transfer with DDR mode, i.e. when DATA[17:16]='3' and DATA[18]='1'. - DATA[7:0] specifies the transmitted Byte. '1'/TX_COUNT: The 'TX_COUNT' command relies on the TX data FIFO to provide the transmitted bytes. - DATA[19] specifies whether this is the last command of a data transfer; i.e. whether the 'spi_select_out[3:0]' IO output signals are de-activated after the transfer. - DATA[18] specifies the mode of transfer rate. - DATA[17:16] specifies the width of the transfer. - DATA[15:0] specifies the number of to be transmitted memory data units (minus 1). '0': 1 unit, '1': 2 units. For SPI (except octal SPI with DDR) one memory data unit is a byte, for octal SPI with DDR and Hyperbus one memory data unit is a 2-byte word. The number of used TX data FIFO entries (in TX_DATA_FIFO_STATUS) = number of memory data units to be transmitted. '2'/RX_COUNT: The 'RX_COUNT' command relies on the RX data FIFO to accept the received bytes. - DATA[19] specifies whether this is the last command of a data transfer; i.e. whether the 'spi_select_out[3:0]' IO output signals are de-activated after the transfer. - DATA[18] specifies the mode of transfer rate. - DATA[17:16] specifies the width of the transfer. - DATA[15:0] specifies the number of to be received memory data units (minus 1). '0': 1 unit, '1': 2 units. For SPI (except octal SPI with DDR) one memory data unit is a byte, for octal SPI with DDR and Hyperbus one memory data unit is a 2-byte word. The number of used RX data FIFO entries (in RX_DATA_FIFO_STATUS) = number of memory data units to be received * 8 / data width (1, 2, 4, 8). The number of used RX data MMIO FIFO entries (in RX_DATA_MMIO_FIFO_STATUS) = number of bytes.

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) '3'/DUMMY_COUNT: The 'DUMMY_COUNT' command conveys dummy cycles. Dummy cycles are used to implement a Turn-Around time in which the SPI master changes from a transmitter driving the data lines to a receiver receiving on the same data lines. The 'DUMMY_COUNT' command is ALWAYS considered to be NOT the last command of a SPI data transfer; i.e. it needs to be followed by another command. - DATA[23] specifies whether RWDS / DQS based capturing is enabled in the last dummy cycle, i.e. this needs to be set to '1' for read transactions to memory device using RWDS / DQS capturing scheme. - DATA[22] specifies whether data learning is enabled. In XIP mode this field is set for read transactions when CTL.INT_CLOCK_DL_ENABLED is '1'. - DATA[21] specifies whether the RWDS output signal should be driven starting in the last dummy cycle until DESELECT. This is needed for write transactions with RWDS (e.g. Hyperbus) before a TX_COUNT command. - DATA[20] specifies whether an active RWDS refresh indicator (captured with the previous rising memory clock output) causes to double the number of dummy cycles. This is used for the variable latency in HyperRAM. - DATA[18] specifies the mode of transfer rate. This is used for data learning and RWDS / DQS capturing. In XIP mode the field is taken from DEVICE.RD_DATA_CTL.DDR_MODE. - DATA[17:16] specifies the width of the transfer. This is used for data learning and RWDS / DQS capturing. In XIP mode the field is taken from DEVICE.RD_DATA_CTL.WIDTH. - DATA[15:0] specifies the number of dummy cycles (minus 1). In dummy cycles, the data lines are not driven. Notes: - If CLOCK_IF_TX_SEL = '0' for transmitting command, address and mode fields in SDR mode (driving data between falling edges of spiwb_clk_out) and the memory is driving read data in DDR mode (based on memory type and transmitted command), then there must be at least 1 latency / dummy cycle specified (DUMMY_COUNT command must be present) to prevent controller and memory driving data signals at the same time. The same is true for the theoretical (practically irrelevant case) of transmitting at least one of the command, address and mode fields in DDR mode but receiving data from the memory in SDR mode. - When using the RWDS / DQS based capturing scheme (CTL.CLK_IF_RX_SEL=[6,7]), then there is a minimum number of latency / dummy cycles required (DUMMY_COUNT command must be present). For the Hyperbus protocol (DDR_CTL.SIZE3=7) at least 1 latency / dummy cycle has to be specified, for SPI with DQS capturing at least 2 latency / dummy cycles need to be selected (RD_DUMMY_CTL.SIZE5 > 0, exception see following note).

Bits	Name	SW	HW	Default or Enum	Description
					(Continuation) - In case of falling edge RWDS / DQS capturing (CTL.CLOCK_IF_RX_SEL = '6') and SDR mode, SW should reduce the number of dummy cycles by 1 compared to the latency cycles required by the memory device. '4'/DESELECT: The 'DESELECT' command deactivates the 'spi' select_out[3:0] IO output signals. The 'DESELECT' command is ALWAYS considered to be the last command of an SPI data transfer. It is used to finish the last transfer of merged continuous transfers.

28.3.6 SMIF_TX_DATA_FIFO_CTL

Description: Transmitter data FIFO control
Address: 0x40420080
Offset: 0x80
Retention: Retained
IsDeepSleep: No
Comment: The TX data FIFO has 8 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					TX_TRIGGER_LEVEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	TX_TRIGGER_LEVEL	RW	RW	0	Determines when the TX data FIFO 'tr_tx_req' trigger is activated (trigger activation requires MMIO_MODE, the trigger is NOT activated in XIP_MODE): - Trigger is active when TX_DATA_FIFO_STATUS.USED <= TRIGGER_LEVEL.

28.3.7 SMIF_TX_DATA_FIFO_STATUS

Description: Transmitter data FIFO status
Address: 0x40420084
Offset: 0x84
Retention: Not Retained
IsDeepSleep: No
Comment: The TX data FIFO has 8 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				USED4 [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	USED4	R	R	0	Number of entries that are used in the TX data FIFO (available in both XIP_MODE and MMIO_MODE). Legal range: [0, 8].

28.3.8 SMIF_TX_DATA_FIFO_WR1

Description: Transmitter data FIFO write

Address: 0x40420090

Offset: 0x90

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides for single byte writes to the TX FIFO. MMIO register accesses must be 32-bit accesses.

Note: In case octal data transfer width and DDR mode (Hyperbus / Octal SPI) has been selected in TX_COUNT command via TX_CMD_FIFO_WR, i.e. 2 bytes are written in one cycle, the lower byte is written with DATA0 and the upper byte is masked (not written). This register must not be used for a word based memory protocol (Hyperbus / Octal SPI) without write byte masking.

A read from this register returns '0'. A write to this register in XIP_MODE results in an AHB-Lite bus error. A write to this register in MMIO_MODE writes the top entry of the FIFO.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	W	W	0	TX data (written to TX data FIFO).

28.3.9 SMIF_TX_DATA_FIFO_WR2

Description: Transmitter data FIFO write

Address: 0x40420094

Offset: 0x94

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides for two simultaneous byte writes to the TX FIFO. MMIO register accesses must be 32-bit accesses.
Note:

A read from this register returns '0'. A write to this register in XIP_MODE results in an AHB-Lite bus error. A write to this register in MMIO_MODE writes the top two entries of the FIFO.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA1 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	W	W	0	TX data (written to TX data FIFO, first byte).
8:15	DATA1	W	W	0	TX data (written to TX data FIFO, second byte).

28.3.10 SMIF_TX_DATA_FIFO_WR4

Description: Transmitter data FIFO write

Address: 0x40420098

Offset: 0x98

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides for four simultaneous byte writes to the TX FIFO. MMIO register accesses must be 32-bit accesses.

A read from this register returns '0'. A write to this register in XIP_MODE results in an AHB-Lite bus error. A write to this register in MMIO_MODE writes the top four entries of the FIFO.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	DATA1 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	DATA2 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	DATA3 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	W	W	0	TX data (written to TX data FIFO, first byte).
8:15	DATA1	W	W	0	TX data (written to TX data FIFO, second byte).
16:23	DATA2	W	W	0	TX data (written to TX data FIFO, third byte).
24:31	DATA3	W	W	0	TX data (written to TX data FIFO, fourth byte).

28.3.11 SMIF_TX_DATA_FIFO_WR1ODD

Description: Transmitter data FIFO write

Address: 0x4042009C

Offset: 0x9C

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides for single byte writes to the TX FIFO for odd byte addresses when using a word based memory protocol (Hyperbus / Octal SPI). MMIO register accesses must be 32-bit accesses.

Note: In case octal data transfer width and DDR mode (Hyperbus / Octal SPI) has been selected in TX_COUNT command via TX_CMD_FIFO_WR, i.e. 2 bytes are written in one cycle, the upper byte is written with DATA0 and the lower byte is masked (not written). This register must not be used for a byte based memory protocol or for a word based memory protocol (Hyperbus / Octal SPI) without write byte masking.

A read from this register returns '0'. A write to this register in XIP_MODE results in an AHB-Lite bus error. A write to this register in MMIO_MODE writes the top entry of the FIFO.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	W	W	0	TX data (written to TX data FIFO).

28.3.12 SMIF_RX_DATA_MMIO_FIFO_CTL

Description: Receiver data MMIO FIFO control
Address: 0x404200C0
Offset: 0xC0
Retention: Retained
IsDeepSleep: No
Comment: The RX data MMIO FIFO has 8 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					RX_TRIGGER_LEVEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	RX_TRIGGER_LEVEL	RW	RW	0	Determines when RX data FIFO 'tr_rx_req' trigger is activated (trigger activation requires MMIO_MODE, the trigger is NOT activated in XIP_MODE): - Trigger is active when RX_DATA_MMIO_FIFO_STATUS.USED > TRIGGER_LEVEL.

28.3.13 SMIF_RX_DATA_MMIO_FIFO_STATUS

Description: Receiver data MMIO FIFO status
Address: 0x404200C4
Offset: 0xC4
Retention: Not Retained
IsDeepSleep: No
Comment: The RX data MMIO FIFO has 8 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:4]				USED4 [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	USED4	R	R	0	Number of entries that are used in the RX data MMIO FIFO (only available in MMIO_MODE). Legal range: [0, 8].

28.3.14 SMIF_RX_DATA_FIFO_STATUS

Description: Receiver data FIFO status
Address: 0x404200C8
Offset: 0xC8
Retention: Not Retained
IsDeepSleep: No
Comment: The RX data FIFO has 16 entries.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			USED5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							RX_SR_USED [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	USED5	R	R	0	Number of entries that are used in the RX data FIFO (available in both XIP_MODE and MMIO_MODE). Legal range: [0, 16].
8	RX_SR_USED	R	R	0	Data available in RX Shift Register, i.e. completely read from RX data FIFO (available in both XIP_MODE and MMIO_MODE).

28.3.15 SMIF_RX_DATA_MMIO_FIFO_RD1

Description: Receiver data MMIO FIFO read

Address: 0x404200D0

Offset: 0xD0

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides a single byte from the RX data MMIO FIFO: a read from this register in MMIO_MODE reads the top entry of the FIFO. MMIO register accesses must be 32-bit accesses.

A write to this register is ignored (no AHB-Lite bus error is generated). A read from this register in XIP_MODE results in an AHB-Lite bus error.

Non test controller read accesses (AHB-Lite bus master identifier is NOT '15') when the RX FIFO is empty behave as specified by CTL.BLOCK and the RX_DATA_FIFO_UNDERFLOW interrupt cause is set to '1'.

Test controller (AHB-Lite bus master identifier is '15') read accesses behave the same as RX_DATA_FIFO_RD1_SILENT read accesses.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	R	R	0	RX data (read from RX data FIFO).

28.3.16 SMIF_RX_DATA_MMIO_FIFO_RD2

Description: Receiver data MMIO FIFO read

Address: 0x404200D4

Offset: 0xD4

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides two bytes from the RX data MMIO FIFO: a read from this register in MMIO_MODE reads the top two entries of the FIFO. MMIO register accesses must be 32-bit accesses.

A write to this register is ignored (no AHB-Lite bus error is generated). A read from this register in XIP_MODE results in an AHB-Lite bus error.

Non test controller read accesses (AHB-Lite bus master identifier is NOT '15') when the RX FIFO is empty behave as specified by CTL.BLOCK and the RX_DATA_FIFO_UNDERFLOW interrupt cause is set to '1'.

Test controller (AHB-Lite bus master identifier is '15') read accesses ALWAYS result in an AHB-Lite bus error. Test controller read accesses do NOT affect the RX_DATA_FIFO_UNDERFLOW interrupt cause.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	R	R	0	RX data (read from RX data FIFO, first byte).
8:15	DATA1	R	R	0	RX data (read from RX data FIFO, second byte).

28.3.17 SMIF_RX_DATA_MMIO_FIFO_RD4

Description: Receiver data MMIO FIFO read

Address: 0x404200D8

Offset: 0xD8

Retention: Not Retained

IsDeepSleep: No

Comment: This register provides four bytes from the RX data MMIO FIFO: a read from this register in MMIO_MODE reads the top four entries of the FIFO. MMIO register accesses must be 32-bit accesses.

A write to this register is ignored (no AHB-Lite bus error is generated). A read from this register in XIP_MODE results in an AHB-Lite bus error.

Non test controller read accesses (AHB-Lite bus master identifier is NOT '15') when the RX FIFO is empty behave as specified by CTL.BLOCK and the RX_DATA_FIFO_UNDERFLOW interrupt cause is set to '1'.

Test controller (AHB-Lite bus master identifier is '15') read accesses ALWAYS result in an AHB-Lite bus error. Test controller read accesses do NOT affect the RX_DATA_FIFO_UNDERFLOW interrupt cause.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DATA1 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DATA2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DATA3 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	R	R	0	RX data (read from RX data FIFO, first byte).
8:15	DATA1	R	R	0	RX data (read from RX data FIFO, second byte).
16:23	DATA2	R	R	0	RX data (read from RX data FIFO, third byte).
24:31	DATA3	R	R	0	RX data (read from RX data FIFO, fourth byte).

28.3.18 SMIF_RX_DATA_MMIO_FIFO_RD1_SILENT

Description: Receiver data MMIO FIFO silent read

Address: 0x404200E0

Offset: 0xE0

Retention: Not Retained

IsDeepSleep: No

Comment: This register is similar to RX_DATA_MMIO_FIFO_RD1, with the exception that the entry is NOT removed from the FIFO. MMIO register accesses must be 32-bit accesses.

A write to this register is ignored (no AHB-Lite bus error is generated). A read from this register in XIP_MODE results in an AHB-Lite bus error.

A read from this register when the RX FIFO is empty results in the return of the value 0xffff_ffff (independent of CTL.BLOCK). Read accesses do NOT affect the RX_DATA_FIFO_UNDERFLOW interrupt cause.

Note: this register is intended to be used by the test controller (AHB-Lite bus master identifier is '15'), but can also be used by other bus masters).

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DATA0 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DATA0	R	R	0	RX data (read from RX data FIFO).

28.3.19 SMIF_SLOW_CA_CTL

Description: Slow cache control

Address: 0x40420100

Offset: 0x100

Retention: Retained

IsDeepSleep: No

Comment: The slow interface/port is used for the CPUSS CM0+, CRYPTO and DataWire components.
Note: cache memory and control information are NOT retained in DeepSleep power mode.

Default: 0xC0000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						WAY [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	PREF_EN [30:30]	None [29:26]				SET_ADDR [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:17	WAY	RW	RW	0	Specifies the cache way for which cache information is provided in SLOW_CA_STATUS0/1/2.
24:25	SET_ADDR	RW	RW	0	Specifies the cache set for which cache information is provided in SLOW_CA_STATUS0/1/2.
30	PREF_EN	RW	RW	1	Prefetch enable: '0': Disabled. '1': Enabled. Prefetching requires the cache to be enabled; i.e. ENABLED is '1'.
31	ENABLED	RW	RW	1	Cache enable: '0': Disabled. '1': Enabled.

28.3.20 SMIF_SLOW_CA_CMD

Description: Slow cache command
Address: 0x40420108
Offset: 0x108
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							INV [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	INV	RW1S	RW1S	0	Cache and prefetch buffer invalidation. SW writes a '1' to clear the cache and prefetch buffer. The cache's LRU structure is also reset to its default state. Note, A write access will invalidate the prefetch buffer automatically in hardware. A write access should invalidate both fast and slow caches, by firmware. Note, firmware should invalidate the cache and prefetch buffer only when STATUS.BUSY is '0'.

28.3.21 SMIF_CRYPT0_CMD

Description: Cryptography Command
Address: 0x40420200
Offset: 0x200
Retention: Not Retained
IsDeepSleep: No
Comment: This register starts an encryption operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							START [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	START	RW1S	RW1S	0	SW sets this field to '1' to start a AES-128 forward block cipher operation (on the address in CRYPTO_ADDR). HW sets this field to '0' to indicate that the operation has completed. Once completed, the result of the operation can be read from CRYPTO_RESULT0, ..., CRYPTO_RESULT3. The operation takes roughly 13 clk_mem clock cycles. Note: An operation can only be started in MMIO_MODE.

28.3.22 SMIF_CRYPTO_INPUT0

Description: Cryptography input 0

Address: 0x40420220

Offset: 0x220

Retention: Not Retained

IsDeepSleep: No

Comment: The CRYPT_INPUT0, ..., CRYPTO_INPUT3 registers provide the plaintext PT[127:0]. The plaintext PT[127:0] is the input to the AES-128 forward block cipher.

These registers are ONLY used in MMIO_MODE. In XIP_MODE, the AHB-Lite bus transfer address CRYPTO_INPUT3, CRYPTO_INPUT2, CRYPTO_INPUT1, A[31:4] and CRYPTO_INPUT0.INPUT[3:0] are used as the plaintext PT[127:0] (the CRYPTO_INPUT0 register is partially used) of the block cipher.

These register should NOT be changed when the IP is busy; i.e. STATUS.BUSY is '1'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INPUT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	INPUT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	INPUT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	INPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INPUT	RW	RW	Undefined	Four Bytes of the plaintext PT[31:0] = CRYPTO_INPUT0.INPUT[31:0].

28.3.23 SMIF_CRYPTO_INPUT1

Description: Cryptography input 1
Address: 0x40420224
Offset: 0x224
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INPUT	RW	RW	Undefined	Four Bytes of the plaintext PT[63:32] = CRYPTO_INPUT1.INPUT[31:0].

28.3.24 SMIF_CRYPTO_INPUT2

Description: Cryptography input 2
Address: 0x40420228
Offset: 0x228
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INPUT	RW	RW	Undefined	Four Bytes of the plaintext PT[95:64] = CRYPTO_INPUT2.INPUT[31:0].

28.3.25 SMIF_CRYPTO_INPUT3

Description: Cryptography input 3
Address: 0x4042022C
Offset: 0x22C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	INPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	INPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	INPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	INPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	INPUT	RW	RW	Undefined	Four Bytes of the plaintext PT[127:96] = CRYPTO_INPUT3.INPUT[31:0].

28.3.26 SMIF_CRYPT0_KEY0

Description: Cryptography key 0

Address: 0x40420240

Offset: 0x240

Retention: Retained

IsDeepSleep: No

Comment: The CRYPTO_KEY3, ..., CRYPTO_KEY0 registers provide the key KEY[127:0]. The key KEY[127:0] is the key of the AES-128 forward block cipher.

SW ALWAYS reads '0' from these registers.

These register should NOT be changed when the IP is busy; i.e. STATUS.BUSY is '1'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	KEY [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	KEY [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	KEY [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	KEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	KEY	W	W	Undefined	Four Bytes of the key KEY[31:0] = CRYPTO_KEY0.KEY[31:0].

28.3.27 SMIF_CRYPT0_KEY1

Description: Cryptography key 1
Address: 0x40420244
Offset: 0x244
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	KEY [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	KEY [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	KEY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	KEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	KEY	W	W	Undefined	Four Bytes of the key KEY[63:32] = CRYPTO_KEY1.KEY[31:0].

28.3.28 SMIF_CRYPT0_KEY2

Description: Cryptography key 2
Address: 0x40420248
Offset: 0x248
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	KEY [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	KEY [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	KEY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	KEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	KEY	W	W	Undefined	Four Bytes of the key KEY[95:64] = CRYPTO_KEY2.KEY[31:0].

28.3.29 SMIF_CRYPT0_KEY3

Description: Cryptography key 3
Address: 0x4042024C
Offset: 0x24C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	KEY [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	KEY [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	KEY [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	KEY [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	KEY	W	W	Undefined	Four Bytes of the key KEY[127:96] = CRYPTO_KEY3.KEY[31:0].

28.3.30 SMIF_CRYPTO_OUTPUT0

Description: Cryptography output 0

Address: 0x40420260

Offset: 0x260

Retention: Not Retained

IsDeepSleep: No

Comment: The CRYPTO_OUTPUT3, ..., CRYPTO_OUTPUT0 registers provide the ciphertext CT[127:0]. The ciphertext CT[127:0] is the output of the AES-128 forward block cipher. The block cipher use the plaintext PT[127:0] as input (CRYPTO_INPUT3, ..., CRYPTO_INPUT0) and key KEY[127:0] as the key (CRYPTO_KEY3, ..., CRYPTO_KEY0).

These registers are ONLY used in MMIO_MODE. In XIP_MODE, the ciphertext CT[127:0] is used (CRYPTO_OUTPUT3, ..., CRYPTO_OUTPUT0 registers are not used) to XOR the plaintext data PD[127:0] (for write operations) or ciphertext CD[127:0] (for read operations).

These register should NOT be changed when the IP is busy; i.e. STATUS.BUSY is '1'.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUTPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	OUTPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	OUTPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	OUTPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	OUTPUT	RW	RW	Undefined	Four Bytes of the ciphertext CT[31:0] = CRYPTO_OUTPUT0.OUTPUT[31:0].

28.3.31 SMIF_CRYPTO_OUTPUT1

Description: Cryptography output 1
Address: 0x40420264
Offset: 0x264
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUTPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	OUTPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	OUTPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	OUTPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	OUTPUT	RW	RW	Undefined	Four Bytes of the ciphertext CT[63:32] = CRYPTO_OUTPUT1.OUTPUT[31:0].

28.3.32 SMIF_CRYPTO_OUTPUT2

Description: Cryptography output 2
Address: 0x40420268
Offset: 0x268
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUTPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	OUTPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	OUTPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	OUTPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	OUTPUT	RW	RW	Undefined	Four Bytes of the ciphertext CT[95:64] = CRYPTO_OUTPUT2.OUTPUT[31:0].

28.3.33 SMIF_CRYPTO_OUTPUT3

Description: Cryptography output 3
Address: 0x4042026C
Offset: 0x26C
Retention: Not Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	OUTPUT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	OUTPUT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	OUTPUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	OUTPUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	OUTPUT	RW	RW	Undefined	Four Bytes of the ciphertext CT[127:96] = CRYPTO_OUTPUT3.OUTPUT[31:0].

28.3.34 SMIF_INTR

Description: Interrupt register
Address: 0x404207C0
Offset: 0x7C0
Retention: Not Retained
IsDeepSleep: No
Comment: The IP has a single Active functionality interrupt. The interrupt causes are described in this register. Interrupt causes are only activated when the IP is enabled; i.e. CTL.ENABLED is '1'.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RX_DATA_MMIO_FIFO_UNDERFLOW [5:5]	TX_DATA_FIFO_OVERFLOW [4:4]	TX_CMD_FIFO_OVERFLOW [3:3]	XIP_ALIGNMENT_ERROR [2:2]	TR_RX_REQ [1:1]	TR_TX_REQ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DL_WARNING [12:12]	None [11:9]			DL_FAIL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FS_STATUS_ERROR [17:17]	CRC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_TX_REQ	RW1C	RW1C	0	Activated in MMIO mode, when a TX data FIFO trigger 'tr_tx_req' is activated.
1	TR_RX_REQ	RW1C	RW1C	0	Activated in MMIO mode, when a RX data FIFO trigger 'tr_rx_req' is activated.

Bits	Name	SW	HW	Default or Enum	Description
2	XIP_ALIGNMENT_ERROR	RW1C	RW1C	0	Activated in XIP mode, when: - a write transfer is requested and - Dual-Quad SPI mode (selected device's ADDR_CTL.DIV2 is '1') is selected or - Octal SPI DDR mode (selected device's DATA_CTL.DDR_MODE = '1' and DATA_CTL.WIDTH = '3') or Hyperbus mode (selected device's ADDR_CTL.SIZE3 = '7') is selected without memory write byte masking (selected device's WR_DUMMY_CTL.RWDS_EN = '0') and - the AHB-Lite / AXI bus transfer address is not a multiple of '2' or - the requested AHB-Lite / AXI bus transfer size is NOT a multiple of '2'. Additionally, it is activated in XIP mode when the selected memory device does not support write byte masking (WR_DUMMY_CTL.RWDS_EN=0) and an AXI transfer occurs with not all of the AXI write strobes ('wstrb') enabled according to the transfer size ('assize'). Note: In dual-quad SPI mode (ADDR_CTL.DIV is '1'), each memory device contributes a 4-bit nibble for read data or write data. Write accesses are only possible if the request address is a multiple of 2 and the number of requested Bytes is a multiple of 2. Octal SPI DDR mode or Hyperbus mode are 16-bit word based protocols, writing single bytes is only possible when write byte masking is supported (via RWDS). Read accesses are always possible by extending the transfer size and / or aligning the address as needed and discarding the non-relevant byte(s).
3	TX_CMD_FIFO_OVERFLOW	RW1C	RW1C	0	Activated in MMIO mode, on an AHB-Lite write transfer to the TX command FIFO (TX_CMD_FIFO_WR) with not enough free entries available.
4	TX_DATA_FIFO_OVERFLOW	RW1C	RW1C	0	Activated in MMIO mode, on an AHB-Lite write transfer to the TX data FIFO (TX_DATA_FIFO_WR1, TX_DATA_FIFO_WR2, TX_DATA_FIFO_WR4) with not enough free entries available.
5	RX_DATA_MMIO_FIFO_UNDERFLOW	RW1C	RW1C	0	Activated in MMIO mode, on an AHB-Lite read transfer from the RX data MMIO FIFO (RX_DATA_MMIO_FIFO_RD1, RX_DATA_MMIO_FIFO_RD2, RX_DATA_MMIO_FIFO_RD4) with not enough entries available. Only activated for NON test bus controller transfers.
8	DL_FAIL	RW1C	RW1C	0	Data Learning Failed (no DLP match found on at least one of the input data lines when CTL.INT_CLOCK_DL_ENABLED = 1).
12	DL_WARNING	RW1C	RW1C	0	Data Learning Warning (for at least one input data line only 1 or 2 delay line taps resulted in a correct DLP capturing when CTL.INT_CLOCK_DL_ENABLED = 1).
16	CRC_ERROR	RW1C	RW1C	0	CRC Error. A read transfer data CRC check failed.
17	FS_STATUS_ERROR	RW1C	RW1C	0	Functional Safety Status Error. A read transfer Functional Safety Status check failed (see definition in DEVICE_ver2.RD_CRC_CTL.STATUS_CHECK_MASK and DEVICE_ver2.RD_CRC_CTL.STATUS_CHECK_MASK_POL).

28.3.35 SMIF_INTR_SET

Description: Interrupt set register

Address: 0x404207C4

Offset: 0x7C4

Retention: Not Retained

IsDeepSleep: No

Comment: When read, this register reflects the interrupt request register. For debug purposes, SW can write a '1' to trigger the cause of an interrupt.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RX_DATA_MMIO_FIFO_UNDERFLOW [5:5]	TX_DATA_FIFO_OVERFLOW [4:4]	TX_CMD_FIFO_OVERFLOW [3:3]	XIP_ALIGNMENT_ERROR [2:2]	TR_RX_REQ [1:1]	TR_TX_REQ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DL_WARNING [12:12]	None [11:9]			DL_FAIL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FS_STATUS_ERROR [17:17]	CRC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_TX_REQ	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	TR_RX_REQ	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	XIP_ALIGNMENT_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
3	TX_CMD_FIFO_OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
4	TX_DATA_FIFO_OVERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
5	RX_DATA_MMIO_FIFO_UNDERFLOW	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
8	DL_FAIL	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
12	DL_WARNING	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
16	CRC_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
17	FS_STATUS_ERROR	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

28.3.36 SMIF_INTR_MASK

Description: Interrupt mask register
Address: 0x404207C8
Offset: 0x7C8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RX_DATA_MMIO_FIFO_UNDERFLOW [5:5]	TX_DATA_FIFO_OVERFLOW [4:4]	TX_CMD_FIFO_OVERFLOW [3:3]	XIP_ALIGNMENT_ERROR [2:2]	TR_RX_REQ [1:1]	TR_TX_REQ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DL_WARNING [12:12]	None [11:9]			DL_FAIL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FS_STATUS_ERROR [17:17]	CRC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_TX_REQ	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	TR_RX_REQ	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	XIP_ALIGNMENT_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
3	TX_CMD_FIFO_OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
4	TX_DATA_FIFO_OVERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
5	RX_DATA_MMIO_FIFO_UNDERFLOW	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
8	DL_FAIL	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
12	DL_WARNING	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
16	CRC_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
17	FS_STATUS_ERROR	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

28.3.37 SMIF_INTR_MASKED

Description: Interrupt masked register
Address: 0x404207CC
Offset: 0x7CC
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise and between the interrupt request and mask registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		RX_DATA_MMIO_FIFO_UNDERFLOW [5:5]	TX_DATA_FIFO_OVERFLOW [4:4]	TX_CMD_FIFO_OVERFLOW [3:3]	XIP_ALIGNMENT_ERROR [2:2]	TR_RX_REQ [1:1]	TR_TX_REQ [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			DL_WARNING [12:12]	None [11:9]			DL_FAIL [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FS_STATUS_ERROR [17:17]	CRC_ERROR [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TR_TX_REQ	R	R	0	Logical and of corresponding request and mask bits.
1	TR_RX_REQ	R	R	0	Logical and of corresponding request and mask bits.
2	XIP_ALIGNMENT_ERROR	R	R	0	Logical and of corresponding request and mask bits.
3	TX_CMD_FIFO_OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
4	TX_DATA_FIFO_OVERFLOW	R	R	0	Logical and of corresponding request and mask bits.
5	RX_DATA_MMIO_FIFO_UNDERFLOW	R	R	0	Logical and of corresponding request and mask bits.
8	DL_FAIL	R	R	0	Logical and of corresponding request and mask bits.
12	DL_WARNING	R	R	0	Logical and of corresponding request and mask bits.
16	CRC_ERROR	R	R	0	Logical and of corresponding request and mask bits.
17	FS_STATUS_ERROR	R	R	0	Logical and of corresponding request and mask bits.

28.3.38 DEVICE

28.3.38.1 SMIF_DEVICE_CTL

Description: Control
Address: 0x40420800
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE (except for the DATA_SEL field, which is used in both the XIP_MODE and MMIO_MODE).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			CRYPTO_EN [4:4]	None [3:1]			WR_EN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	MERGE_EN [15:15]	MERGE_TIMEOUT [14:12]			None [11:10]			DATA_SEL [9:8]

Bits	23	22	21	20	19	18	17	16
Name	TOTAL_TIMEOUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	TOTAL_TIMEOUT_EN [30:30]	TOTAL_TIMEOUT [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WR_EN	RW	RW	0	Write enable: '0': write transfers are not allowed to this device. An attempt to write to this device results in an AHB-Lite bus error. '1': write transfers are allowed to this device.
4	CRYPTO_EN	RW	RW	0	Cryptography on read/write accesses: '0': disabled. '1': enabled.
8:9	DATA_SEL	RW	RW	0	Specifies the connection of the IP's data lines (spi_data[0], ..., spi_data[7]) to the device's data lines (SI/IO0, SO/IO1, IO2, IO3, IO4, IO5, IO6, IO7): '0': spi_data[0] = IO0, spi_data[1] = IO1, ..., spi_data[7] = IO7. This value is allowed for single, dual, quad, dual quad and octal SPI modes. This value must be used for the first device in dual quad SPI mode. This value must be used for octal SPI mode. '1': spi_data[2] = IO0, spi_data[3] = IO1. This value is only allowed for single and dual SPI modes. '2': spi_data[4] = IO0, spi_data[5] = IO1, ..., spi_data[7] = IO3. This value is only allowed for single, dual, quad and dual quad SPI modes. In dual quad SPI mode, this value must be used for the second device. '3': spi_data[6] = IO0, spi_data[7] = IO1. This value is only allowed for single and dual SPI modes.

Bits	Name	SW	HW	Default or Enum	Description
12:14	MERGE_TIMEOUT	RW	RW	0	Continuous transfer merge timeout in clk_mem cycles. This limits the standby time of the memory interface, i.e. the time the memory device is selected but no data is transferred. The counting of the merge timeout period is done in the XIP block using clk_mem cycles. It starts when the last TX or RX byte is transferred to or from the data FIFOs. After this period the memory device is deselected. A later transfer, even from a continuous address, starts with the overhead phases (command, address, mode, dummy cycles).
	_1_cycle			0	Timeout after 1 clk_mem cycle. That means transfers will only be merged if the continuous transfer request is already available when the previous transfer is finished.
	_16_cycles			1	Timeout after $2^4 = 16$ clk_mem cycles. At a clk_mem frequency of 200MHz this means 80ns.
	_256_cycles			2	Timeout after $2^8 = 256$ clk_mem cycles. At a clk_mem frequency of 200MHz this means ~1.3us.
	_4096_cycles			3	Timeout after $2^{12} = 4096$ clk_mem cycles. At a clk_mem frequency of 200MHz this means ~20us.
	_65536_cycles			4	Timeout after $2^{16} = 65536$ clk_mem cycles. At a clk_mem frequency of 200MHz this means ~330us.
	Reserved5			5	N/A
	Reserved6			6	N/A
	Reserved7			7	N/A
15	MERGE_EN	RW	RW	0	Continuous transfer merge enable: '0': Disabled. No merging of transfers is done. Longest possible memory transfer is 16 Byte. '1': Enabled. Merging of continuous transfers is done. This skips the overhead (command, address, mode, dummy cycles) for a continuous (linear sequential) transfer.

Bits	Name	SW	HW	Default or Enum	Description
16:29	TOTAL_TIMEOUT	RW	RW	0	Total transfer timeout in clk_mem cycles. The counting of the total timeout period is done in the XIP block using clk_mem cycles. It starts when the first command of a new (not merged) transaction is transferred to the TX command FIFO causing the interface logic to select the memory. After this period the memory device is deselected. This feature is needed for RAM devices requiring refresh cycles. The value needs to be derived from the RAMs maximum transaction length time (tCMS) minus the time of transferring 2x16byte data block (data granularity of the XIP ports is 16byte, 1 16byte block transfer outstanding, another available for merging). If the result is negative, MERGE_EN must be set to '0'. Example: RAM device tCMS = 4us, interface clock frequency = 100MHz: total transfer timeout is 4us - 2x16x10ns = 3680ns. With clk_mem frequency of 200MHz the TOTAL_TIMEOUT value is 3680/5 = 736. Note: In the unlikely case that the total transfer timeout is used (usually for RAM devices) while the page boundary crossing latency generation is enabled via RD_BOUND_CTL.PRESENT (usually for FLASH devices) the additional time needs to be taken into account.
30	TOTAL_TIMEOUT_EN	RW	RW	0	Total transfer timeout enable. '0': Disabled. There is no limit for the total transfer time. The continuous transfer merge timeout for limiting the idle time of the memory interface still applies. '1': Enabled. The maximum total transfer time is limited by field TOTAL_TIMEOUT.
31	ENABLED	RW	RW	0	Device enable: '0': Disabled. '1': Enabled.

28.3.38.2 SMIF_DEVICE_ADDR

Description: Device region base address
Address: 0x40420808
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	ADDR [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ADDR [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ADDR [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:31	ADDR	RW	RW	Undefined	Specifies the base address of the device region. If the device region is 2^m Bytes, ADDR MUST be a multiple of 2^m. In dual quad SPI data transfer, the two devices should have the same ADDR and MASK register settings. The device control information (ADDR_CTL, RD_CMD_CTL, etc.) are provided by the MMIO control registers of the device with the lowest index. The most significant bit fields are constants and set based on the SMIF_XIP_ADDR parameter. The most significant bits are identified on the SMIF_XIP_MASK parameter. E.g., if SMIF_XIP_MASK is 0xff00:0000 (16 MB XIP memory region), ADDR[31:24] = SMIF_XIP_ADDR[31:24].

28.3.38.3 SMIF_DEVICE_MASK

Description: Device region mask
Address: 0x4042080C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	MASK [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	MASK [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	MASK [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:31	MASK	RW	RW	Undefined	Specifies the size of the device region. All '1' bits are used to compare the incoming transfer request address A[31:0] with the address as specified in ADDR.ADDR: Address A is in the device when (A[31:8] & MASK[31:8]) == ADDR.ADDR[31:8]. The most significant bit fields are constants and set to '1'. The most significant bits are identified on the SMIF_XIP_MASK parameter. E.g., if SMIF_XIP_MASK is 0xff00:0000 (16 MB XIP memory region), MASK[31:24] = 0xff. Note: a transfer request that is not in any device region results in an AHB-Lite bus error.

28.3.38.4 SMIF_DEVICE_ADDR_CTL

Description: Address control
Address: 0x40420820
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					SIZE3 [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							DIV2 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	SIZE3	RW	RW	0	Specifies the size of the XIP device address in Bytes: '0': 1 Byte address. '1': 2 Byte address. '2': 3 Byte address. '3': 4 Byte address. '4'-'6': These settings are reserved. Do not use. '7': 4 Byte address (spread over 5 bytes) according to Hyperbus protocol. The lower significant address Bytes of the transfer request are used as XIP address to the external device. Note that for dual quad SPI data transfer, the XIP transfer request address is divided by 2. Therefore, the XIP transfer request address needs to be a multiple of 2. If the address is NOT a multiple of 2, the XIP_ALIGNMENT_ERROR interrupt cause is activated. Note: If Hyperbus protocol is selected (SIZE3='7') then the WIDTH field must be set to '3' (octal data transfer) and the DDR_MODE field must be set to '1' (DDR mode) in the read/write command and address control registers, and the PRESENT field in read/write command control registers need be set to '1' (1 command byte).

Bits	Name	SW	HW	Default or Enum	Description
8	DIV2	RW	RW	0	Specifies if the AHB-Lite bus transfer address is divided by 2 or not: '0': No divide by 2. '1': Divide by 2. This functionality is used for read and write operation in XIP, dual quad SPI mode; i.e. this DIV2 must be set to '1' in dual quad SPI mode. If DIV2 is set to '1', the memory does not support write masking (WR_DUMMY_CTL.RWDS_EN = '0'), and in this configuration a write transfer is requested and the write transfer request address is NOT a multiple of 2 or the requested number of Bytes to be written is not a multiple of 2, the XIP_ALIGNMENT_ERROR interrupt cause is activated.

28.3.38.5 SMIF_DEVICE_RD_CMD_CTL

Description: Read command control
Address: 0x40420840
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CODE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CODEH [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CODE	RW	RW	0	Command byte code.
8:15	CODEH	RW	RW	0	Command high byte code. This field specifies the most significant command byte, sent before the least significant command byte (CODE). It is only used when PRESENT2 = '2'.
16:17	WIDTH	RW	RW	0	Width of data transfer: '0': 1 bit/cycle (single data transfer). '1': 2 bits/cycle (dual data transfer). '2': 4 bits/cycle (quad data transfer). '3': 8 bits/cycle (octal data transfer).
18	DDR_MODE	RW	RW	0	Mode of transfer rate: '0': SDR mode '1': DDR mode
30:31	PRESENT2	RW	RW	0	Presence of command field: '0': not present '1': present (1 Byte) '2': present (2 Byte for OPI) Note: For octal data transfer with DDR mode (WIDTH='3' and DDR_MODE='1') either the HB protocol needs to be selected (by ADDR_CTL.SIZE3='7') or this field needs to be set to PRESENT2='2'.

28.3.38.6 SMIF_DEVICE_RD_ADDR_CTL

Description: Read address control
Address: 0x40420844
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.

28.3.38.7 SMIF_DEVICE_RD_MODE_CTL

Description: Read mode control
Address: 0x40420848
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CODE [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CODEH [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CODE	RW	RW	0	Mode byte code. Note: If a mode field is present (PRESENT='1') for octal data transfer with DDR mode (WIDTH='3' and DDR_MODE='1') the CODE is sent twice.
8:15	CODEH	RW	RW	0	Mode high byte code. This field specifies the most significant mode byte, sent before the least significant mode byte (CODE). It is only used when PRESENT2 = '2'.
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.
30:31	PRESENT2	RW	RW	0	Presence of mode field: '0': not present '1': present (1 Byte) '2': present (2 Byte for OPI) Note: For octal data transfer with DDR mode (WIDTH='3' and DDR_MODE='1') this field needs to be set to PRESENT2='2' to generate a mode field (or to PRESENT2='0').

28.3.38.8 SMIF_DEVICE_RD_DUMMY_CTL

Description: Read dummy control
Address: 0x4042084C
Offset: 0x4C
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SIZE5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	SIZE5	RW	RW	0	Number of dummy cycles (minus 1): '0': 1 cycles ... '31': 32 cycles. Note: this field specifies dummy cycles, not dummy Bytes!

Bits	Name	SW	HW	Default or Enum	Description
30:31	PRESENT2	RW	RW	0	Presence of dummy cycles: '0': not present '1': present '2': present - Dummy cycles are doubled when RWDS refresh indicator is high during CA cycle. (HyperRAM variable latency mode) Notes: - If CLOCK_IF_TX_SEL = '0' for transmitting command, address and mode fields in SDR mode (driving data between falling edges of spi_hb_clk_out) and the memory is driving read data in DDR mode (based on memory type and transmitted command), then there must be at least 1 latency / dummy cycle specified (RD_DUMMY_CTL.PRESENT2 > 0) to prevent controller and memory driving data signals at the same time. - The same is true for the theoretical (practically irrelevant case) of transmitting at least one of the command, address and mode fields in DDR mode but receiving data from the memory in SDR mode. - When using the RWDS / DQS based capturing scheme (CTL.CLK_IF_RX_SEL=[6,7]), then there is a minimum number of latency / dummy cycles required (RD_DUMMY_CTL.PRESENT2 > 0). For the Hyperbus protocol (DDR_CTL.SIZE3=7) at least 1 latency / dummy cycle has to be specified, for SPI with DQS capturing at least 2 latency / dummy cycles need to be selected (RD_DUMMY_CTL.SIZE5 > 0, exception see following note). - In case of falling edge RWDS / DQS capturing (CTL.CLOCK_IF_RX_SEL = '6') and SDR mode, SW should reduce the number of dummy cycles by 1 compared to the latency cycles required by the memory device. - For Hyperbus, set RD_DUMMY_CTL.SIZE5=initial latency cycles-2

28.3.38.9 SMIF_DEVICE_RD_DATA_CTL

Description: Read data control
Address: 0x40420850
Offset: 0x50
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.

28.3.38.10 SMIF_DEVICE_RD_BOUND_CTL

Description: Read boundary control
Address: 0x40420858
Offset: 0x58
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x100000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SIZE5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		SUB_PAGE_NR [21:20]		None [19:18]		SUB_PAGE_SIZE [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	PRESENT [31:31]	None [30:29]		SUBSEQ_BOUND_EN [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	SIZE5	RW	RW	0	Number of base latency cycles (minus 1) used for calculating the number of first page boundary crossing latency cycles: '0': base_latency = 1 cycles ... '31': base_latency = 32 cycles. The actual latency cycles when crossing the first page boundary depend on the start address of the transaction and is calculated as follows: if ((page_size - base_latency) < Start_Addr & (sub_page_size - 1)) { ((Start_Addr & (sub_page_size - 1)) - page_size + base_latency) } else { 0 }
16:17	SUB_PAGE_SIZE	RW	RW	0	Specifies the size of a memory sub page 'sub_page_size'. '0': sub_page_size = 8 words = 16 bytes (default). '1': sub_page_size = 16 words = 32 bytes. '2': sub_page_size = 32 words = 64 bytes. '3': sub_page_size = 64 words = 128 bytes.
20:21	SUB_PAGE_NR	RW	RW	1	Specifies the number of sub pages per page. '0': 1 sub pages per page, i.e. page_size = sub_page_size '1': 2 sub pages per page, i.e. page_size = 2 x sub_page_size '2': 4 sub pages per page, i.e. page_size = 4 x sub_page_size '3': 8 sub pages per page, i.e. page_size = 8 x sub_page_size

Bits	Name	SW	HW	Default or Enum	Description
28	SUBSEQ_BOUND_EN	RW	RW	0	Enable subsequent page boundary latency cycles. '0': Disabled. The page crossing latency cycles are only generated when crossing the first page boundary (i.e. the first time when the SUB_PAGE_NRth sub page boundary is crossed, e.g. with 2 sub pages per page when the 2nd sub page boundary is crossed). '1': Enabled. The page crossing latency cycles are generated when crossing the first and subsequent page boundaries (i.e. every time when a SUB_PAGE_NRth sub page boundary is crossed, e.g. with 2 sub pages per page when the 2nd, 4th, 6th, ... sub page boundary is crossed). Note: This only applies when the number of base latency cycles (SIZE5+1) is greater than the size of a page (base_latency > page_size).
31	PRESENT	RW	RW	0	Presence of first page boundary latency cycles: '0': not present '1': present

28.3.38.11 SMIF_DEVICE_WR_CMD_CTL

Description: Write command control
Address: 0x40420860
Offset: 0x60
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CODE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CODEH [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CODE	RW	RW	0	Command byte code.
8:15	CODEH	RW	RW	0	Command high byte code. This field specifies the most significant command byte, sent before the least significant command byte (CODE). It is only used when PRESENT2 = '2'.
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.
30:31	PRESENT2	RW	RW	0	Presence of command field: '0': not present '1': present (1 Byte) '2': present (2 Byte for OPI) Note: For octal data transfer with DDR mode (WIDTH='3' and DDR_MODE='1') either the HB protocol needs to be selected (by ADDR_CTL.SIZE3='7') or this field needs to be set to PRESENT2='2'.

28.3.38.12 SMIF_DEVICE_WR_ADDR_CTL

Description: Write address control
Address: 0x40420864
Offset: 0x64
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.

28.3.38.13 SMIF_DEVICE_WR_MODE_CTL

Description: Write mode control
Address: 0x40420868
Offset: 0x68
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CODE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CODEH [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CODE	RW	RW	0	Mode byte code.
8:15	CODEH	RW	RW	0	Mode high byte code. This field specifies the most significant mode byte, sent before the least significant mode byte (CODE). It is only used when PRESENT2 = '2'.
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.
30:31	PRESENT2	RW	RW	0	Presence of mode field: '0': not present '1': present (1 Byte) '2': present (2 Byte for OPI) Note: For octal data transfer with DDR mode (WIDTH='3' and DDR_MODE='1') this field needs to be set to PRESENT2='2' to generate a mode field (or to PRESENT2='0').

28.3.38.14 SMIF_DEVICE_WR_DUMMY_CTL

Description: Write dummy control
Address: 0x4042086C
Offset: 0x6C
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			SIZE5 [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						RWDS_EN [17:17]	None [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PRESENT2 [31:30]		None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	SIZE5	RW	RW	0	Number of dummy cycles (minus 1): '0': 1 cycles ... '31': 32 cycles.
17	RWDS_EN	RW	RW	0	Read-Write-Data-Strobe Enable. Specifies whether the RWDS output signal should be driven starting in the last dummy cycle until DESELECT. This is needed for write transactions with byte masking via RWDS (e.g. Hyperbus). '0': do not drive RWDS output '1': drive RWDS output starting in last dummy cycle until DESELECT Note: this field is located in the WR_DUMMY_CTL register (and not in the WR_DATA_CTL register) since the RWDS signal needs to be driven already in the last dummy cycle.
30:31	PRESENT2	RW	RW	0	Presence of dummy cycles: '0': not present '1': present '2': present - Dummy cycles are doubled when RWDS refresh indicator is high during CA cycle. (HyperRAM variable latency mode)

28.3.38.15 SMIF_DEVICE_WR_DATA_CTL

Description: Write data control
Address: 0x40420870
Offset: 0x70
Retention: Retained
IsDeepSleep: No
Comment: This register is only used in XIP_MODE.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					DDR_MODE [18:18]	WIDTH [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
16:17	WIDTH	RW	RW	0	Width of transfer.
18	DDR_MODE	RW	RW	0	Mode of transfer rate.

29 SRSS

Description SRSS Core Registers (ver3)
Base Address 0x40260000
Size 0x10000
Slave Num MMIO2 - 5

Register Name	Address	Permission	Description
PWR_LVD_STATUS	0x40260040	FULL	High Voltage / Low Voltage Detector (HVLVD) Status Register
PWR_LVD_STATUS2	0x40260044	FULL	High Voltage / Low Voltage Detector (HVLVD) Status Register #2
CLK_DSI_SELECT0	0x40260100	FULL	Clock DSI Select Register
CLK_DSI_SELECT1	0x40260104	FULL	Clock DSI Select Register
CLK_DSI_SELECT2	0x40260108	FULL	Clock DSI Select Register
CLK_DSI_SELECT3	0x4026010C	FULL	Clock DSI Select Register
CLK_DSI_SELECT4	0x40260110	FULL	Clock DSI Select Register
CLK_DSI_SELECT5	0x40260114	FULL	Clock DSI Select Register
CLK_DSI_SELECT6	0x40260118	FULL	Clock DSI Select Register
CLK_OUTPUT_FAST	0x40260140	FULL	Fast Clock Output Select Register
CLK_OUTPUT_SLOW	0x40260144	FULL	Slow Clock Output Select Register
CLK_CAL_CNT1	0x40260148	FULL	Clock Calibration Counter 1
CLK_CAL_CNT2	0x4026014C	FULL	Clock Calibration Counter 2
SRSS_INTR	0x40260200	FULL	SRSS Interrupt Register
SRSS_INTR_SET	0x40260204	FULL	SRSS Interrupt Set Register
SRSS_INTR_MASK	0x40260208	FULL	SRSS Interrupt Mask Register
SRSS_INTR_MASKED	0x4026020C	FULL	SRSS Interrupt Masked Register
PWR_CTL	0x40261000	FULL	Power Mode Control
PWR_CTL2	0x40261004	FULL	Power Mode Control 2 <i>Note: LINREG_LPMODE RET_REG_DIS NWEELL_REG_DIS REFV_OK REFVBUFF_LPMODE REFI_LPMODE PORBOD_LPMODE are not available for this register</i>
PWR_HIBERNATE	0x40261008	FULL	HIBERNATE Mode Register
PWR_SSV_CTL	0x40261018	FULL	Supply Supervision Control Register
PWR_SSV_STATUS	0x4026101C	FULL	Supply Supervision Status Register
PWR_LVD_CTL	0x40261020	FULL	High Voltage / Low Voltage Detector (HVLVD) Configuration Register <i>Note: HVLVD1_TRIPSEL HVLVD1_SRCSEL HVLVD1_EN are not available for this register</i>
PWR_LVD_CTL2	0x40261024	FULL	High Voltage / Low Voltage Detector (HVLVD) Configuration Register #2
PWR_REGHC_CTL	0x40261028	FULL	REGHC Control Register
PWR_REGHC_STATUS	0x4026102C	FULL	REGHC Status Register
PWR_REGHC_CTL2	0x40261030	FULL	REGHC Control Register 2
PWR_REGHC_CTL4	0x40261038	FULL	REGHC Control Register 4
PWR_HIB_DATA0	0x40261040	FULL	HIBERNATE Data Register
CLK_PATH_SELECT0	0x40261200	FULL	Clock Path Select Register
CLK_PATH_SELECT1	0x40261204	FULL	Clock Path Select Register
CLK_PATH_SELECT2	0x40261208	FULL	Clock Path Select Register
CLK_PATH_SELECT3	0x4026120C	FULL	Clock Path Select Register
CLK_PATH_SELECT4	0x40261210	FULL	Clock Path Select Register
CLK_PATH_SELECT5	0x40261214	FULL	Clock Path Select Register
CLK_PATH_SELECT6	0x40261218	FULL	Clock Path Select Register
CLK_ROOT_SELECT0	0x40261240	FULL	Clock Root Select Register
CLK_ROOT_SELECT1	0x40261244	FULL	Clock Root Select Register
CLK_ROOT_SELECT2	0x40261248	FULL	Clock Root Select Register
CLK_ROOT_SELECT3	0x4026124C	FULL	Clock Root Select Register
CLK_ROOT_SELECT4	0x40261250	FULL	Clock Root Select Register
CLK_ROOT_SELECT5	0x40261254	FULL	Clock Root Select Register
CLK_ROOT_SELECT6	0x40261258	FULL	Clock Root Select Register
CLK_ROOT_SELECT7	0x4026125C	FULL	Clock Root Select Register
CLK_SELECT	0x40261500	FULL	Clock selection register
CLK_TIMER_CTL	0x40261504	FULL	Timer Clock Control Register

Register Name	Address	Permission	Description
CLK_ILO0_CONFIG	0x40261508	FULL	ILO0 Configuration
CLK_ILO1_CONFIG	0x4026150C	FULL	ILO1 Configuration
CLK_IMO_CONFIG	0x40261518	FULL	IMO Configuration
CLK_ECO_CONFIG	0x4026151C	FULL	ECO Configuration Register
CLK_ECO_PRESCALE	0x40261520	FULL	ECO Prescaler Configuration Register
CLK_ECO_STATUS	0x40261524	FULL	ECO Status Register
CLK_FLL_CONFIG	0x40261530	FULL	FLL Configuration Register
CLK_FLL_CONFIG2	0x40261534	FULL	FLL Configuration Register 2
CLK_FLL_CONFIG3	0x40261538	FULL	FLL Configuration Register 3
CLK_FLL_CONFIG4	0x4026153C	FULL	FLL Configuration Register 4
CLK_FLL_STATUS	0x40261540	FULL	FLL Status Register
CLK_ECO_CONFIG2	0x40261544	FULL	ECO Configuration Register 2
CLK_PLL_CONFIG0	0x40261600	FULL	PLL Configuration Register
CLK_PLL_CONFIG1	0x40261604	FULL	PLL Configuration Register
CLK_PLL_STATUS0	0x40261640	FULL	PLL Status Register
CLK_PLL_STATUS1	0x40261644	FULL	PLL Status Register
CSV_REF_SEL	0x40261700	FULL	Select CSV Reference clock for Active domain
RES_CAUSE	0x40261800	FULL	Reset Cause Observation Register
RES_CAUSE2	0x40261804	FULL	Reset Cause Observation Register 2
CLK_TRIM_ILO0_CTL	0x40263014	READ	ILO0 Trim Register
CLK_TRIM_ILO1_CTL	0x40263220	READ	ILO1 Trim Register

29.1 CSV_HF

29.1.1 CSV 0

Register Name	Address	Permission	Description
CSV_HF_CSV0_REF_CTL	0x40261400	FULL	Clock Supervision Reference Control
CSV_HF_CSV0_REF_LIMIT	0x40261404	FULL	Clock Supervision Reference Limits
CSV_HF_CSV0_MON_CTL	0x40261408	FULL	Clock Supervision Monitor Control

29.1.2 CSV 1

Register Name	Address	Permission	Description
CSV_HF_CSV1_REF_CTL	0x40261410	FULL	Clock Supervision Reference Control
CSV_HF_CSV1_REF_LIMIT	0x40261414	FULL	Clock Supervision Reference Limits
CSV_HF_CSV1_MON_CTL	0x40261418	FULL	Clock Supervision Monitor Control

29.1.3 CSV 2

Register Name	Address	Permission	Description
CSV_HF_CSV2_REF_CTL	0x40261420	FULL	Clock Supervision Reference Control
CSV_HF_CSV2_REF_LIMIT	0x40261424	FULL	Clock Supervision Reference Limits
CSV_HF_CSV2_MON_CTL	0x40261428	FULL	Clock Supervision Monitor Control

29.1.4 CSV 3

Register Name	Address	Permission	Description
CSV_HF_CSV3_REF_CTL	0x40261430	FULL	Clock Supervision Reference Control
CSV_HF_CSV3_REF_LIMIT	0x40261434	FULL	Clock Supervision Reference Limits
CSV_HF_CSV3_MON_CTL	0x40261438	FULL	Clock Supervision Monitor Control

29.1.5 CSV 4

Register Name	Address	Permission	Description
CSV_HF_CSV4_REF_CTL	0x40261440	FULL	Clock Supervision Reference Control
CSV_HF_CSV4_REF_LIMIT	0x40261444	FULL	Clock Supervision Reference Limits
CSV_HF_CSV4_MON_CTL	0x40261448	FULL	Clock Supervision Monitor Control

29.1.6 CSV 5

Register Name	Address	Permission	Description
CSV_HF_CSV5_REF_CTL	0x40261450	FULL	Clock Supervision Reference Control
CSV_HF_CSV5_REF_LIMIT	0x40261454	FULL	Clock Supervision Reference Limits
CSV_HF_CSV5_MON_CTL	0x40261458	FULL	Clock Supervision Monitor Control

29.1.7 CSV 6

Register Name	Address	Permission	Description
CSV_HF_CSV6_REF_CTL	0x40261460	FULL	Clock Supervision Reference Control

Register Name	Address	Permission	Description
CSV_HF_CSV6_REF_LIMIT	0x40261464	FULL	Clock Supervision Reference Limits
CSV_HF_CSV6_MON_CTL	0x40261468	FULL	Clock Supervision Monitor Control

29.1.8 CSV 7

Register Name	Address	Permission	Description
CSV_HF_CSV7_REF_CTL	0x40261470	FULL	Clock Supervision Reference Control
CSV_HF_CSV7_REF_LIMIT	0x40261474	FULL	Clock Supervision Reference Limits
CSV_HF_CSV7_MON_CTL	0x40261478	FULL	Clock Supervision Monitor Control

29.2 CSV_REF

29.2.1 CSV

Register Name	Address	Permission	Description
CSV_REF_CSV_REF_CTL	0x40261710	FULL	Clock Supervision Reference Control
CSV_REF_CSV_REF_LIMIT	0x40261714	FULL	Clock Supervision Reference Limits
CSV_REF_CSV_MON_CTL	0x40261718	FULL	Clock Supervision Monitor Control

29.3 CSV_LF

29.3.1 CSV

Register Name	Address	Permission	Description
CSV_LF_CSV_REF_CTL	0x40261720	FULL	Clock Supervision Reference Control
CSV_LF_CSV_REF_LIMIT	0x40261724	FULL	Clock Supervision Reference Limits
CSV_LF_CSV_MON_CTL	0x40261728	FULL	Clock Supervision Monitor Control

29.4 CSV_ILO

29.4.1 CSV

Register Name	Address	Permission	Description
CSV_ILO_CSV_REF_CTL	0x40261730	FULL	Clock Supervision Reference Control
CSV_ILO_CSV_REF_LIMIT	0x40261734	FULL	Clock Supervision Reference Limits
CSV_ILO_CSV_MON_CTL	0x40261738	FULL	Clock Supervision Monitor Control

29.5 CLK_PLL400M 0

Register Name	Address	Permission	Description
CLK_PLL400M0_CONFIG	0x40261900	FULL	400MHz PLL Configuration Register
CLK_PLL400M0_CONFIG2	0x40261904	FULL	400MHz PLL Configuration Register 2
CLK_PLL400M0_CONFIG3	0x40261908	FULL	400MHz PLL Configuration Register 3
CLK_PLL400M0_STATUS	0x4026190C	FULL	400MHz PLL Status Register

29.6 CLK_PLL400M 1

Register Name	Address	Permission	Description
CLK_PLL400M1_CONFIG	0x40261910	FULL	400MHz PLL Configuration Register
CLK_PLL400M1_CONFIG2	0x40261914	FULL	400MHz PLL Configuration Register 2
CLK_PLL400M1_CONFIG3	0x40261918	FULL	400MHz PLL Configuration Register 3
CLK_PLL400M1_STATUS	0x4026191C	FULL	400MHz PLL Status Register

29.7 MCWDT 0

Register Name	Address	Permission	Description
MCWDT0_CPU_SELECT	0x40268040	FULL	MCWDT CPU selection register
MCWDT0_CTR2_CTL	0x40268080	FULL	MCWDT Subcounter 2 Control register
MCWDT0_CTR2_CONFIG	0x40268084	FULL	MCWDT Subcounter 2 Configuration register
MCWDT0_CTR2_CNT	0x40268088	FULL	MCWDT Subcounter 2 Count Register
MCWDT0_LOCK	0x40268090	FULL	MCWDT Lock Register
MCWDT0_SERVICE	0x40268094	FULL	MCWDT Service Register
MCWDT0_INTR	0x402680A0	FULL	MCWDT Interrupt Register
MCWDT0_INTR_SET	0x402680A4	FULL	MCWDT Interrupt Set Register
MCWDT0_INTR_MASK	0x402680A8	FULL	MCWDT Interrupt Mask Register
MCWDT0_INTR_MASKED	0x402680AC	FULL	MCWDT Interrupt Masked Register

29.7.1 CTR 0

Register Name	Address	Permission	Description
MCWDT0_CTR0_CTL	0x40268000	FULL	MCWDT Subcounter Control Register
MCWDT0_CTR0_LOWER_LIMIT	0x40268004	FULL	MCWDT Subcounter Lower Limit Register
MCWDT0_CTR0_UPPER_LIMIT	0x40268008	FULL	MCWDT Subcounter Upper Limit Register
MCWDT0_CTR0_WARN_LIMIT	0x4026800C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT0_CTR0_CONFIG	0x40268010	FULL	MCWDT Subcounter Configuration Register
MCWDT0_CTR0_CNT	0x40268014	FULL	MCWDT Subcounter Count Register

29.7.2 CTR 1

Register Name	Address	Permission	Description
MCWDT0_CTR1_CTL	0x40268020	FULL	MCWDT Subcounter Control Register
MCWDT0_CTR1_LOWER_LIMIT	0x40268024	FULL	MCWDT Subcounter Lower Limit Register
MCWDT0_CTR1_UPPER_LIMIT	0x40268028	FULL	MCWDT Subcounter Upper Limit Register
MCWDT0_CTR1_WARN_LIMIT	0x4026802C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT0_CTR1_CONFIG	0x40268030	FULL	MCWDT Subcounter Configuration Register
MCWDT0_CTR1_CNT	0x40268034	FULL	MCWDT Subcounter Count Register

29.8 MCWDT 1

Register Name	Address	Permission	Description
MCWDT1_CPU_SELECT	0x40268140	FULL	MCWDT CPU selection register
MCWDT1_CTR2_CTL	0x40268180	FULL	MCWDT Subcounter 2 Control register
MCWDT1_CTR2_CONFIG	0x40268184	FULL	MCWDT Subcounter 2 Configuration register
MCWDT1_CTR2_CNT	0x40268188	FULL	MCWDT Subcounter 2 Count Register
MCWDT1_LOCK	0x40268190	FULL	MCWDT Lock Register
MCWDT1_SERVICE	0x40268194	FULL	MCWDT Service Register
MCWDT1_INTR	0x402681A0	FULL	MCWDT Interrupt Register
MCWDT1_INTR_SET	0x402681A4	FULL	MCWDT Interrupt Set Register
MCWDT1_INTR_MASK	0x402681A8	FULL	MCWDT Interrupt Mask Register
MCWDT1_INTR_MASKED	0x402681AC	FULL	MCWDT Interrupt Masked Register

29.8.1 CTR 0

Register Name	Address	Permission	Description
MCWDT1_CTR0_CTL	0x40268100	FULL	MCWDT Subcounter Control Register
MCWDT1_CTR0_LOWER_LIMIT	0x40268104	FULL	MCWDT Subcounter Lower Limit Register
MCWDT1_CTR0_UPPER_LIMIT	0x40268108	FULL	MCWDT Subcounter Upper Limit Register
MCWDT1_CTR0_WARN_LIMIT	0x4026810C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT1_CTR0_CONFIG	0x40268110	FULL	MCWDT Subcounter Configuration Register
MCWDT1_CTR0_CNT	0x40268114	FULL	MCWDT Subcounter Count Register

29.8.2 CTR 1

Register Name	Address	Permission	Description
MCWDT1_CTR1_CTL	0x40268120	FULL	MCWDT Subcounter Control Register
MCWDT1_CTR1_LOWER_LIMIT	0x40268124	FULL	MCWDT Subcounter Lower Limit Register
MCWDT1_CTR1_UPPER_LIMIT	0x40268128	FULL	MCWDT Subcounter Upper Limit Register
MCWDT1_CTR1_WARN_LIMIT	0x4026812C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT1_CTR1_CONFIG	0x40268130	FULL	MCWDT Subcounter Configuration Register
MCWDT1_CTR1_CNT	0x40268134	FULL	MCWDT Subcounter Count Register

29.9 MCWDT 2

Register Name	Address	Permission	Description
MCWDT2_CPU_SELECT	0x40268240	FULL	MCWDT CPU selection register
MCWDT2_CTR2_CTL	0x40268280	FULL	MCWDT Subcounter 2 Control register
MCWDT2_CTR2_CONFIG	0x40268284	FULL	MCWDT Subcounter 2 Configuration register
MCWDT2_CTR2_CNT	0x40268288	FULL	MCWDT Subcounter 2 Count Register
MCWDT2_LOCK	0x40268290	FULL	MCWDT Lock Register
MCWDT2_SERVICE	0x40268294	FULL	MCWDT Service Register
MCWDT2_INTR	0x402682A0	FULL	MCWDT Interrupt Register
MCWDT2_INTR_SET	0x402682A4	FULL	MCWDT Interrupt Set Register
MCWDT2_INTR_MASK	0x402682A8	FULL	MCWDT Interrupt Mask Register
MCWDT2_INTR_MASKED	0x402682AC	FULL	MCWDT Interrupt Masked Register

29.9.1 CTR 0

Register Name	Address	Permission	Description
MCWDT2_CTR0_CTL	0x40268200	FULL	MCWDT Subcounter Control Register
MCWDT2_CTR0_LOWER_LIMIT	0x40268204	FULL	MCWDT Subcounter Lower Limit Register
MCWDT2_CTR0_UPPER_LIMIT	0x40268208	FULL	MCWDT Subcounter Upper Limit Register
MCWDT2_CTR0_WARN_LIMIT	0x4026820C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT2_CTR0_CONFIG	0x40268210	FULL	MCWDT Subcounter Configuration Register
MCWDT2_CTR0_CNT	0x40268214	FULL	MCWDT Subcounter Count Register

29.9.2 CTR 1

Register Name	Address	Permission	Description
MCWDT2_CTR1_CTL	0x40268220	FULL	MCWDT Subcounter Control Register
MCWDT2_CTR1_LOWER_LIMIT	0x40268224	FULL	MCWDT Subcounter Lower Limit Register
MCWDT2_CTR1_UPPER_LIMIT	0x40268228	FULL	MCWDT Subcounter Upper Limit Register
MCWDT2_CTR1_WARN_LIMIT	0x4026822C	FULL	MCWDT Subcounter Warn Limit Register
MCWDT2_CTR1_CONFIG	0x40268230	FULL	MCWDT Subcounter Configuration Register
MCWDT2_CTR1_CNT	0x40268234	FULL	MCWDT Subcounter Count Register

29.10 WDT

Register Name	Address	Permission	Description
WDT_CTL	0x4026C000	FULL	WDT Control Register
WDT_LOWER_LIMIT	0x4026C004	FULL	WDT Lower Limit Register
WDT_UPPER_LIMIT	0x4026C008	FULL	WDT Upper Limit Register
WDT_WARN_LIMIT	0x4026C00C	FULL	WDT Warn Limit Register
WDT_CONFIG	0x4026C010	FULL	WDT Configuration Register
WDT_CNT	0x4026C014	FULL	WDT Count Register
WDT_LOCK	0x4026C040	FULL	WDT Lock register
WDT_SERVICE	0x4026C044	FULL	WDT Service register
WDT_INTR	0x4026C050	FULL	WDT Interrupt Register
WDT_INTR_SET	0x4026C054	FULL	WDT Interrupt Set Register
WDT_INTR_MASK	0x4026C058	FULL	WDT Interrupt Mask Register
WDT_INTR_MASKED	0x4026C05C	FULL	WDT Interrupt Masked Register

29.11 Register Details

29.11.1 PWR_LVD_STATUS

Description: High Voltage / Low Voltage Detector (HVLVD) Status Register
Address: 0x40260040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: Real-time status for Voltage Monitoring System
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							HVLVD1_OUT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	HVLVD1_OUT	R	R	0	HVLVD1 output. 0: below voltage threshold 1: above voltage threshold

29.11.2 PWR_LVD_STATUS2

Description: High Voltage / Low Voltage Detector (HVLVD) Status Register #2
Address: 0x40260044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: Real-time status for Voltage Monitoring System
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							HVLVD2_OUT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	HVLVD2_OUT	R	R	0	HVLVD2 output. 0: below voltage threshold 1: above voltage threshold

29.11.3 CLK_DSI_SELECT

Description: Clock DSI Select Register

Address: 0x40260100

Offset: 0x100

Retention: Retained

IsDeepSleep: Yes

Comment: Configures DSI mux in clock generation path. Each path has its own copy of this register. See PAS for DSI signal connectivity list.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			DSI_MUX [4:0]				

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:4	DSI_MUX	RW	RW	0	Selects a DSI source or low frequency clock for use in a clock path. The output of this mux can be selected for clock PATH<i></i> using CLK_PATH_SELECT register. Using the output of this mux as HFCLK source will result in undefined behavior. It can be used to clocks to DSI or as reference inputs for the FLL/PLL, subject to the frequency limits of those circuits. This mux is not glitch free, so do not change the selection while it is an actively selected clock.
	DSI_OUT0			0	DSI0 - dsi_out[0]
	DSI_OUT1			1	DSI1 - dsi_out[1]
	DSI_OUT2			2	DSI2 - dsi_out[2]
	DSI_OUT3			3	DSI3 - dsi_out[3]
	DSI_OUT4			4	DSI4 - dsi_out[4]
	DSI_OUT5			5	DSI5 - dsi_out[5]
	DSI_OUT6			6	DSI6 - dsi_out[6]
	DSI_OUT7			7	DSI7 - dsi_out[7]
	DSI_OUT8			8	DSI8 - dsi_out[8]
	DSI_OUT9			9	DSI9 - dsi_out[9]
	DSI_OUT10			10	DSI10 - dsi_out[10]
	DSI_OUT11			11	DSI11 - dsi_out[11]
	DSI_OUT12			12	DSI12 - dsi_out[12]
	DSI_OUT13			13	DSI13 - dsi_out[13]
	DSI_OUT14			14	DSI14 - dsi_out[14]
	DSI_OUT15			15	DSI15 - dsi_out[15]
	ILO0			16	ILO0 - Internal Low-speed Oscillator #0
	WCO			17	WCO - Watch-Crystal Oscillator
	ALTTF			18	ALTTF - Alternate Low-Frequency Clock
	PILO			19	PILO - Precision Internal Low-speed Oscillator
	ILO1			20	ILO1 - Internal Low-speed Oscillator #1, if present.

29.11.4 CLK_OUTPUT_FAST

Description: Fast Clock Output Select Register
Address: 0x40260140
Offset: 0x140
Retention: Retained
IsDeepSleep: Yes
Comment: Selects clocks for calibration
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PATH_SEL0 [7:4]				FAST_SEL0 [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				HFCLK_SEL0 [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	PATH_SEL1 [23:20]				FAST_SEL1 [19:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				HFCLK_SEL1 [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FAST_SEL0	RW	RW	0	Select signal for fast clock output #0
	NC			0	Disabled - output is 0. For power savings, clocks are blocked before entering any muxes, including PATH_SEL0 and HFCLK_SEL0.
	ECO			1	External Crystal Oscillator (ECO)
	EXTCLK			2	External clock input (EXTCLK)
	ALTHF			3	Alternate High-Frequency (ALTHF) clock input to SRSS
	TIMERCLK			4	Timer clock. It is grouped with the fast clocks because it may be a gated version of a fast clock, and therefore may have a short high pulse.
	PATH_SEL0			5	Selects the clock path chosen by PATH_SEL0 field
	HFCLK_SEL0			6	Selects the output of the HFCLK_SEL0 mux
4:7	SLOW_SEL0			7	Selects the output of CLK_OUTPUT_SLOW.SLOW_SEL0
	PATH_SEL0	RW	RW	0	Selects a clock path to use in fast clock output #0 logic. 0: FLL output 1-15: PLL output on path1-path15 (if available)
8:11	HFCLK_SEL0	RW	RW	0	Selects a HFCLK tree for use in fast clock output #0
16:19	FAST_SEL1	RW	RW	0	Select signal for fast clock output #1
	NC			0	Disabled - output is 0. For power savings, clocks are blocked before entering any muxes, including PATH_SEL1 and HFCLK_SEL1.
	ECO			1	External Crystal Oscillator (ECO)
	EXTCLK			2	External clock input (EXTCLK)
	ALTHF			3	Alternate High-Frequency (ALTHF) clock input to SRSS
	TIMERCLK			4	Timer clock. It is grouped with the fast clocks because it may be a gated version of a fast clock, and therefore may have a short high pulse.
	PATH_SEL1			5	Selects the clock path chosen by PATH_SEL1 field
	HFCLK_SEL1			6	Selects the output of the HFCLK_SEL1 mux

Bits	Name	SW	HW	Default or Enum	Description
	SLOW_SEL1			7	Selects the output of CLK_OUTPUT_SLOW.SLOW_SEL1
20:23	PATH_SEL1	RW	RW	0	Selects a clock path to use in fast clock output #1 logic. 0: FLL output 1-15: PLL output on path1-path15 (if available)
24:27	HFCLK_SEL1	RW	RW	0	Selects a HFCLK tree for use in fast clock output #1 logic

29.11.5 CLK_OUTPUT_SLOW

Description: Slow Clock Output Select Register
Address: 0x40260144
Offset: 0x144
Retention: Retained
IsDeepSleep: Yes
Comment: Selects a slow clock for calibration. The outputs of these muxes go into CLK_OUTPUT_FAST.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SLOW_SEL1 [7:4]				SLOW_SEL0 [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	SLOW_SEL0	RW	RW	0	Select signal for slow clock output #0
	NC			0	Disabled - output is 0. For power savings, clocks are blocked before entering any muxes.
	ILO0			1	Internal Low Speed Oscillator (ILO0)
	WCO			2	Watch-Crystal Oscillator (WCO)
	BAK			3	Root of the Backup domain clock tree (BAK)
	ALTLF			4	Alternate low-frequency clock input to SRSS (ALTLF)
	LFCLK			5	Root of the low-speed clock tree (LFCLK)
	IMO			6	Internal Main Oscillator (IMO). This is grouped with the slow clocks so it can be observed during DEEPSLEEP entry/exit.
	SLPCTRL			7	Sleep Controller clock (SLPCTRL). This is grouped with the slow clocks so it can be observed during DEEPSLEEP entry/exit.
	PILO			8	Precision Internal Low Speed Oscillator (PILO)
	ILO1			9	Internal Low Speed Oscillator (ILO1), if present on the product.
	ECO_PRESCALER			10	ECO Prescaler (ECO_PRESCALER)
	LPECO			11	LPECO
	LPECO_PRESCALER			12	LPECO Prescaler (LPECO_PRESCALER)
4:7	SLOW_SEL1	RW	RW	0	Select signal for slow clock output #1
	NC			0	Disabled - output is 0. For power savings, clocks are blocked before entering any muxes.
	ILO0			1	Internal Low Speed Oscillator (ILO)
	WCO			2	Watch-Crystal Oscillator (WCO)
	BAK			3	Root of the Backup domain clock tree (BAK)
	ALTLF			4	Alternate low-frequency clock input to SRSS (ALTLF)
	LFCLK			5	Root of the low-speed clock tree (LFCLK)
	IMO			6	Internal Main Oscillator (IMO). This is grouped with the slow clocks so it can be observed during DEEPSLEEP entry/exit.

Bits	Name	SW	HW	Default or Enum	Description
	SLPCTRL			7	Sleep Controller clock (SLPCTRL). This is grouped with the slow clocks so it can be observed during DEEPSLEEP entry/exit.
	PILO			8	Precision Internal Low Speed Oscillator (PILO)
	ILO1			9	Internal Low Speed Oscillator (ILO1), if present on the product.
	ECO_PRESCALER			10	ECO Prescaler (ECO_PRESCALER)
	LPECO			11	LPECO
	LPECO_PRESCALER			12	LPECO Prescaler (LPECO_PRESCALER)

29.11.6 CLK_CAL_CNT1

Description: Clock Calibration Counter 1
Address: 0x40260148
Offset: 0x148
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x80000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CAL_COUNTER1 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CAL_COUNTER1 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	CAL_COUNTER1 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CAL_COUNTER_DONE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	CAL_COUNTER1	RW	RW	0	Down-counter clocked on fast clock output #0 (see CLK_OUTPUT_FAST). This register always reads as zero. Counting starts internally when this register is written with a nonzero value. CAL_COUNTER_DONE goes immediately low to indicate that the counter has started and will be asserted when the counters are done. Do not write this field unless CAL_COUNTER_DONE==1. Both clocks must be running or the measurement will not complete. A stalled counter can be recovered by selecting valid clocks, waiting until the measurement completes, and discarding the first result.
31	CAL_COUNTER_DONE	R	R	1	Status bit indicating that the internal counter #1 is finished counting and CLK_CAL_CNT2.COUNTER stopped counting up

29.11.7 CLK_CAL_CNT2

Description: Clock Calibration Counter 2
Address: 0x4026014C
Offset: 0x14C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CAL_COUNTER2 [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CAL_COUNTER2 [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CAL_COUNTER2 [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	CAL_COUNTER2	R	R	0	Up-counter clocked on fast clock output #1 (see CLK_OUTPUT_FAST). When CLK_CAL_CNT1.CAL_COUNTER_DONE==1, the counter is stopped and can be read by SW. Do not read this value unless CAL_COUNTER_DONE==1. The expected final value is related to the ratio of clock frequencies used for the two counters and the value loaded into counter 1: $\text{CLK\_CAL\_CNT2.COUNTER} = (\text{F\_cnt2} / \text{F\_cnt1}) * (\text{CLK\_CAL\_CNT1.COUNTER})$

29.11.8 SRSS_INTR

Description: SRSS Interrupt Register
Address: 0x40260200
Offset: 0x200
Retention: Retained
IsDeepSleep: Yes
Comment: Interrupt signal from SRSS includes this register and also BACKUP_INTR, if present.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CLK_CAL [5:5]	None [4:3]		HVLVD2 [2:2]	HVLVD1 [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	HVLVD1	RW1C	RW1C	0	Interrupt for low voltage detector HVLVD1
2	HVLVD2	RW1C	RW1C	0	Interrupt for low voltage detector HVLVD2
5	CLK_CAL	RW1C	RW1C	0	Clock calibration counter is done. This field is reset during DEEPSLEEP mode.

29.11.9 SRSS_INTR_SET

Description: SRSS Interrupt Set Register
Address: 0x40260204
Offset: 0x204
Retention: Retained
IsDeepSleep: Yes
Comment: Can be used to set interrupts for firmware testing.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CLK_CAL [5:5]	None [4:3]		HVLVD2 [2:2]	HVLVD1 [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	HVLVD1	RW1S	RW1S	0	Set interrupt for low voltage detector HVLVD1
2	HVLVD2	RW1S	RW1S	0	Set interrupt for low voltage detector HVLVD2
5	CLK_CAL	RW1S	RW1S	0	Set interrupt for clock calibration counter done. This field is reset during DEEPSLEEP mode.

29.11.10 SRSS_INTR_MASK

Description: SRSS Interrupt Mask Register
Address: 0x40260208
Offset: 0x208
Retention: Retained
IsDeepSleep: Yes
Comment: Controls whether interrupt is forwarded to CPU. All masks block the interrupt when 0 and forward the interrupt when 1
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CLK_CAL [5:5]	None [4:3]		HVLVD2 [2:2]	HVLVD1 [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	HVLVD1	RW	RW	0	Mask for low voltage detector HVLVD1
2	HVLVD2	RW	RW	0	Mask for low voltage detector HVLVD2
5	CLK_CAL	RW	RW	0	Mask for clock calibration done

29.11.11 SRSS_INTR_MASKED

Description: SRSS Interrupt Masked Register
Address: 0x4026020C
Offset: 0x20C
Retention: Retained
IsDeepSleep: Yes
Comment: Bitwise and between the interrupt request and mask registers so firmware can read the status of all mask enabled interrupt causes with a single load operation
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CLK_CAL [5:5]	None [4:3]		HVLVD2 [2:2]	HVLVD1 [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	HVLVD1	R	R	0	Logical and of corresponding request and mask bits.
2	HVLVD2	R	R	0	Logical and of corresponding request and mask bits.
5	CLK_CAL	R	R	0	Logical and of corresponding request and mask bits.

29.11.12 PWR_CTL

Description: Power Mode Control
Address: 0x40261000
Offset: 0x1000
Retention: Retained
IsDeepSleep: Yes
Comment: Controls the device power mode options and allows observation of current state.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		LPM_READY [5:5]	DEBUG_SESSION [4:4]	None [3:2]		POWER_MODE [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	POWER_MODE	R	R	0	Current power mode of the device. Note that this field cannot be read in all power modes on actual silicon.
	RESET			0	System is resetting.
	ACTIVE			1	At least one CPU is running.
	SLEEP			2	No CPUs are running. Peripherals may be running.
	DEEPSLEEP			3	Main high-frequency clock is off; low speed clocks are available. Communication interface clocks may be present.
4	DEBUG_SESSION	R	R	0	Indicates whether a debug session is active (CDBGPWRUPREQ signal is 1)
	NO_SESSION			0	No debug session active
	SESSION_ACTIVE			1	Debug session is active. Power modes behave differently to keep the debug session active.
5	LPM_READY	R	R	0	Indicates whether certain low power functions are ready. The low current circuits take longer to startup after XRES, HIBERNATE wakeup, or supply supervision reset wakeup than the normal mode circuits. HIBERNATE mode may be entered regardless of this bit. 0: If a low power circuit operation is requested, it will stay in its normal operating mode until it is ready. If DEEPSLEEP is requested by all processors WFI/WFE, the device will instead enter SLEEP. When low power circuits are ready, device will automatically enter the originally requested mode. 1: Normal operation. DEEPSLEEP and low power circuits operate as requested in other registers.

29.11.13 PWR_CTL2

Description: Power Mode Control 2
Address: 0x40261004
Offset: 0x1004
Retention: Retained
IsDeepSleep: Yes
Comment: Controls the device power mode options and allows observation of current state.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			DPSLP_REG_DIS [4:4]	None [3:3]	LINREG_LPMODE [2:2]	LINREG_OK [1:1]	LINREG_DIS [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			NWELL_REG_DIS [12:12]	None [11:9]			RET_REG_DIS [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:23]	REFVBUF_LPMODE [22:22]	REFVBUF_OK [21:21]	REFVBUF_DIS [20:20]	None [19:18]		REFV_OK [17:17]	REFV_DIS [16:16]

Bits	31	30	29	28	27	26	25	24
Name	PLL_LS_BY_PASS [31:31]	None [30:29]		BGREF_LPMODE [28:28]	PORBOD_LPMODE [27:27]	REFI_LPMODE [26:26]	REFI_OK [25:25]	REFI_DIS [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LINREG_DIS	RW	RW	0	Explicitly disable the linear Core Regulator. Write zero for Traveo II devices. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: Linear Core Regulator is not explicitly disabled. Hardware disables it automatically for internal sequences, including for DEEPSLEEP, HIBERNATE, and XRES low power modes. 1: Linear Core Regulator is explicitly disabled. Only use this for special cases when another source supplies vccd during ACTIVE and SLEEP modes. This setting is only legal when another source supplies vccd, but there is no special hardware protection for this case.
1	LINREG_OK	R	R	0	Status of the linear Core Regulator.
2	LINREG_LPMODE	RW	RW	0	Control the power mode of the Linear Regulator. The value in this register is ignored and normal mode is used until LPM_READY==1. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: Linear Regulator operates in normal mode. Internal current consumption is 50uA and load current capability is 50mA to 300mA, depending on the number of regulator modules present in the product. 1: Linear Regulator operates in low power mode. Internal current consumption is 5uA and load current capability is 25mA. Firmware must ensure the current is kept within the limit.

Bits	Name	SW	HW	Default or Enum	Description
4	DPSLP_REG_DIS	RW	RW	0	Explicitly disable the DeepSleep regulator, including circuits shared with the Active Regulator. This register must not be set except as part of a Cypress-provided sequence or API, such as the PMIC case described below. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. If the DeepSleep regulator is disabled, it is not supported to enable it again later by clearing this bit. 0: DeepSleep Regulator is not explicitly disabled. This is the normal setting, and hardware automatically controls the DeepSleep regulator for most sequences, including for HIBERNATE and XRES low power modes. This setting must be used if the Active Linear Regulator is used, because some circuitry is shared. 1: DeepSleep Regulator is explicitly disabled. Only use this for special cases when another source supplies vccdpslp during DEEPSLEEP mode and there is no future intention to use the Active Regulator for ACTIVE/SLEEP modes. For example, this setting is used as part of a Cypress-provided handover sequence to a PMIC that operates in ACTIVE, SLEEP, and DEEPSLEEP and disables both the Active Linear Regulator and DeepSleep Regulator.
8	RET_REG_DIS	RW	RW	0	Explicitly disable the Retention regulator. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: Retention Regulator is not explicitly disabled. Hardware disables it automatically for internal sequences, including for HIBERNATE and XRES low power modes. Hardware keeps the Retention Regulator enabled during ACTIVE/SLEEP modes, so it is ready to enter DEEPSLEEP at any time. 1: Retention Regulator is explicitly disabled. Only use this for special cases when another source supplies vccret during DEEPSLEEP mode. This setting is only legal when another source supplies vccret, but there is no special hardware protection for this case.
12	NWELL_REG_DIS	RW	RW	0	Explicitly disable the Nwell regulator. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: Nwell Regulator is on. Hardware disables it automatically for internal sequences, including for HIBERNATE and XRES low power modes. Hardware keeps the Nwell Regulator enabled during ACTIVE/SLEEP modes, so it is ready to enter DEEPSLEEP at any time. 1: Nwell Regulator is explicitly disabled. Only use this for special cases when another source supplies vnwell during DEEPSLEEP mode. This setting is only legal when another source supplies vnwell, but there is no special hardware protection for this case.
16	REFV_DIS	RW	RW	0	Disables the voltage reference. PSoC products: This disables the Active voltage reference. Firmware must ensure that LPM_READY==1 and BGREF_LPMODE==1 for at least 1us before disabling the Active Reference. When enabling the Active Reference, use REFV_OK indicator to know when it is ready. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. Traveo II products: Reserved. Write zero.

Bits	Name	SW	HW	Default or Enum	Description
17	REFV_OK	R	R	0	Indicates that the normal mode of the voltage reference is ready.
20	REFVBUF_DIS	RW	RW	0	Disable the voltage reference buffer. Firmware should only disable the buffer when there is no connected circuit that is using it. SRSS circuits that require it are the PLL and ECO. A particular product may have circuits outside the SRSS that use the buffer. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset.
21	REFVBUF_OK	R	R	0	Indicates that the voltage reference buffer is ready. Due to synchronization delays, it may take two IMO clock cycles for hardware to clear this bit after asserting REFVBUF_DIS=1.
22	REFVBUF_LPMODE	RW	RW	0	Control the power mode of the 800mV voltage reference buffer. The value in this register is ignored and normal mode is used until LPM_READY==1. 0: Voltage Reference Buffer operates in normal mode. They work for vddd ramp rates of 100mV/us or less. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 1: Voltage Reference Buffer operates in low power mode. Power supply rejection is reduced to save current, and they work for vddd ramp rates of 10mV/us or less.
24	REFI_DIS	RW	RW	0	Reserved. Write zero.
25	REFI_OK	R	R	0	Indicates that the current reference is ready. Due to synchronization delays, it may take two IMO clock cycles for hardware to clear this bit after asserting REFI_DIS=1.
26	REFI_LPMODE	RW	RW	0	Control the power mode of the reference current generator. The value in this register is ignored and normal mode is used until LPM_READY==1. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: Current reference generator operates in normal mode. It works for vddd ramp rates of 100mV/us or less. 1: Current reference generator operates in low power mode. Response time is reduced to save current, and it works for vddd ramp rates of 10mV/us or less.
27	PORBOD_LPMODE	RW	RW	0	Control the power mode of the POR/BOD circuits. The value in this register is ignored and normal mode is used until LPM_READY==1. This register is only reset by XRES, HIBERNATE wakeup, or supply supervision reset. 0: POR/BOD circuits operate in normal mode. They work for vddd ramp rates of 100mV/us or less. 1: POR/BOD circuits operate in low power mode. Response time is reduced to save current, and they work for vddd ramp rates of 10mV/us or less.
28	BGREF_LPMODE	RW	RW	0	Control the circuit-level power mode of the Bandgap Reference circuits. 0: Bandgap Reference circuits operate in higher current mode. 1: Bandgap Reference circuits operate in low power. Refer to documentation for restrictions.

Bits	Name	SW	HW	Default or Enum	Description
31	PLL_LS_BYPASS	RW	RW	0	Bypass level shifter inside the PLL. Unused, if no PLL is present in the product. 0: Do not bypass the level shifter. This setting is ok for all operational modes and vccd target voltage. 1: Bypass the level shifter. This may reduce jitter on the PLL output clock, but can only be used when vccd is targeted to 1.1V nominal. Otherwise, it can result in clock degradation and static current.

29.11.14 PWR_HIBERNATE

Description: HIBERNATE Mode Register

Address: 0x40261008

Offset: 0x1008

Retention: Retained

IsDeepSleep: No

Comment: This register controls entry/exit from HIBERNATE power mode. This register is implemented in the unregulated voltage domain. This register and PWR_HIB_DATA registers are the only ones that continue to retain information during HIBERNATE mode. Three identical writes are required to enter HIBERNATE mode. Ensure changes settle after the third write by reading this register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TOKEN [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	UNLOCK [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	POLARITY_HIBPIN [23:20]				MASK_HIBWDT [19:19]	MASK_HIBALARM [18:18]	FREEZE [17:17]	None [16:16]
Bits	31	30	29	28	27	26	25	24
Name	HIBERNATE [31:31]	HIBERNATE_DISABLE [30:30]	None [29:28]		MASK_HIBPIN [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	TOKEN	RW	RW	0	Contains a 8-bit token that is retained through a HIBERNATE/WAKEUP sequence that can be used by firmware to differentiate WAKEUP from a general RESET event. Note that waking up from HIBERNATE using XRES will reset this register.
8:15	UNLOCK	RW	RW	0	This byte must be set to 0x3A for FREEZE or HIBERNATE fields to operate. Any other value in this register will cause FREEZE/HIBERNATE to have no effect, except as noted in the FREEZE description.
17	FREEZE	RW	RW	0	Firmware sets this bit to freeze the configuration, mode and state of all GPIOs and SIOs in the system. When entering HIBERNATE mode, the first write instructs DEEPSLEEP peripherals that they cannot ignore the upcoming freeze command. This occurs even in the illegal condition where UNLOCK is not set. If UNLOCK and HIBERNATE are properly set, the IOs actually freeze on the second write. Supply supervision is disabled during HIBERNATE mode. HIBERNATE peripherals ignore resets (excluding XRES) while FREEZE==1.
18	MASK_HIBALARM	RW	RW	0	When set, HIBERNATE will wakeup for a RTC interrupt
19	MASK_HIBWDT	RW	RW	0	When set, HIBERNATE will wakeup for WDT interrupt

Bits	Name	SW	HW	Default or Enum	Description
20:23	POLARITY_HIBPIN	RW	RW	0	Each bit sets the active polarity of the corresponding wakeup pin. 0: Pin input of 0 will wakeup the part from HIBERNATE 1: Pin input of 1 will wakeup the part from HIBERNATE
24:27	MASK_HIBPIN	RW	RW	0	When set, HIBERNATE will wakeup if the corresponding pin input matches the POLARITY_HIBPIN setting. Each bit corresponds to one of the wakeup pins.
30	HIBERNATE_DISABLE	RW1S	RW1S	0	Hibernate disable bit. 0: Normal operation, HIBERNATE works as described 1: Further writes to this register are ignored Note: This bit is a write-once bit until the next reset. Avoid changing any other bits in this register while disabling HIBERNATE mode. Also, it is recommended to clear the UNLOCK code, if it was previously written..
31	HIBERNATE	RW	RW	0	Firmware sets this bit to enter HIBERNATE mode. The system will enter HIBERNATE mode immediately after writing to this bit and will wakeup only in response to XRES or WAKEUP event. Both UNLOCK and FREEZE must have been set correctly in a previous write operations. Otherwise, it will not enter HIBERNATE. External supplies must have been stable for 250us before entering HIBERNATE mode.

29.11.15 PWR_SSV_CTL

Description: Supply Supervision Control Register
Address: 0x40261018
Offset: 0x1018
Retention: Retained
IsDeepSleep: Yes
Comment: Controls for brownout and over-voltage detectors. Fields *_VSEL and *_ACTION are only reset by XRES/POR/BOD/OVD/OCD/HIBERNATE. Fields *_ENABLE are reset by all resets.
Default: 0x8080808

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	BODVDDA_ACTION [7:6]		None [5:5]	BODVDDA_VSEL [4:4]	BODVDDD_ENABLE [3:3]	None [2:1]		BODVDDD_VSEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				BODVCCD_ENABLE [11:11]	None [10:9]		BODVDDA_ENABLE [8:8]

Bits	23	22	21	20	19	18	17	16
Name	OVDVDDA_ACTION [23:22]		None [21:21]	OVDVDDA_VSEL [20:20]	OVDVDDD_ENABLE [19:19]	None [18:17]		OVDVDDD_VSEL [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:28]				OVDVCCD_ENABLE [27:27]	None [26:25]		OVDVDDA_ENABLE [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BODVDDD_VSEL	RW	RW	0	Selects the voltage threshold for BOD on vddd. The BOD does not reliably monitor the supply during the transition. 0: vddd<2.7V 1: vddd<3.0V
3	BODVDDD_ENABLE	RW	RW	1	Enable for BOD on vddd. This cannot be disabled during normal operation.
4	BODVDDA_VSEL	RW	RW	0	Selects the voltage threshold for BOD on vdda. Ensure BODVDDA_ENABLE==0 before changing this setting to prevent false triggers. 0: vdda<2.7V 1: vdda<3.0V
6:7	BODVDDA_ACTION	RW	RW	0	Action taken when the BOD on vdda triggers.
	NOTHING			0	No action
	FAULT			1	Generate a fault
	RESET			2	Reset the chip
8	BODVDDA_ENABLE	RW	RW	0	Enable for BOD on vdda. BODVDDA_ACTION will be triggered when the BOD is disabled. If no action is desired when disabling, firmware must first write BODVDDA_ACTION=NOTHING in a separate write cycle.
11	BODVCCD_ENABLE	RW	RW	1	Enable for BOD on vccd. This cannot be disabled during normal operation.

Bits	Name	SW	HW	Default or Enum	Description
16	OVDVDDD_VSEL	RW	RW	0	Selects the voltage threshold for OVD on vddd. The OVD does not reliably monitor the supply during the transition. 0: vddd>5.5V 1: vddd>5.0V
19	OVDVDDD_ENABLE	RW	RW	1	Enable for OVD on vddd. This cannot be disabled during normal operation.
20	OVDVDDA_VSEL	RW	RW	0	Selects the voltage threshold for OVD on vdda. Ensure OVDVDDA_ENABLE==0 before changing this setting to prevent false triggers 0: vddd>5.5V 1: vddd>5.0V
22:23	OVDVDDA_ACTION	RW	RW	0	Action taken when the OVD on vdda triggers.
	NOTHING			0	No action
	FAULT			1	Generate a fault
	RESET			2	Reset the chip
24	OVDVDDA_ENABLE	RW	RW	0	Enable for OVD on vdda.
27	OVDVCCD_ENABLE	RW	RW	1	Enable for OVD on vccd. This cannot be disabled during normal operation.

29.11.16 PWR_SSV_STATUS

Description: Supply Supervision Status Register
Address: 0x4026101C
Offset: 0x101C
Retention: Retained
IsDeepSleep: Yes
Comment: Status for brownout and over-voltage detectors.
Default: 0x30505

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					BODVCCD_OK [2:2]	BODVDDA_OK [1:1]	BODVDDD_OK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					OVDVCCD_OK [10:10]	OVDVDDA_OK [9:9]	OVDVDDD_OK [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						OCD_DPSLP_REG_OK [17:17]	OCD_ACT_LINREG_OK [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	BODVDDD_OK	R	R	1	BOD indicates vddd is ok. This will always read 1, because a detected brownout will reset the chip.
1	BODVDDA_OK	R	R	0	BOD indicates vdda is ok.
2	BODVCCD_OK	R	R	1	BOD indicates vccd is ok. This will always read 1, because a detected brownout will reset the chip.
8	OVDVDDD_OK	R	R	1	OVD indicates vddd is ok. This will always read 1, because a detected over-voltage condition will reset the chip.
9	OVDVDDA_OK	R	R	0	OVD indicates vdda is ok.
10	OVDVCCD_OK	R	R	1	OVD indicates vccd is ok. This will always read 1, because a detected over-over-voltage condition will reset the chip.
16	OCD_ACT_LINREG_OK	R	R	1	OCD indicates the current drawn from the linear Active Regulator is ok. This will always read 1, because a detected over-current condition will reset the chip.
17	OCD_DPSLP_REG_OK	R	R	1	OCD indicates the current drawn from the linear DeepSleep Regulator is ok. This will always read 1, because a detected over-current condition will reset the chip.

29.11.17 PWR_LVD_CTL

Description: High Voltage / Low Voltage Detector (HVLVD) Configuration Register
Address: 0x40261020
Offset: 0x1020
Retention: Retained
IsDeepSleep: Yes
Comment: Trim and configuration bits for Voltage Monitoring System.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	HVLVD1_EN [7:7]	HVLVD1_SRCSEL [6:4]			HVLVD1_TRIPSEL [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	HVLVD1_EN_HT [15:15]	HVLVD1_DPSLP_EN_HT [14:14]	None [13:13]	HVLVD1_TRIPSEL_HT [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					HVLVD1_ACTION [18:18]	HVLVD1_EDGE_SEL [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	HVLVD1_TRIPSEL	RW	RW	0	Threshold selection for HVLVD1. Disable the detector (HVLVD1_EN=0) before changing the threshold. 0: rise=1.225V (nom), fall=1.2V (nom) 1: rise=1.425V (nom), fall=1.4V (nom) 2: rise=1.625V (nom), fall=1.6V (nom) 3: rise=1.825V (nom), fall=1.8V (nom) 4: rise=2.025V (nom), fall=2V (nom) 5: rise=2.125V (nom), fall=2.1V (nom) 6: rise=2.225V (nom), fall=2.2V (nom) 7: rise=2.325V (nom), fall=2.3V (nom) 8: rise=2.425V (nom), fall=2.4V (nom) 9: rise=2.525V (nom), fall=2.5V (nom) 10: rise=2.625V (nom), fall=2.6V (nom) 11: rise=2.725V (nom), fall=2.7V (nom) 12: rise=2.825V (nom), fall=2.8V (nom) 13: rise=2.925V (nom), fall=2.9V (nom) 14: rise=3.025V (nom), fall=3.0V (nom) 15: rise=3.125V (nom), fall=3.1V (nom)
4:6	HVLVD1_SRCSEL	RW	RW	0	Source selection for HVLVD1
	VDDD			0	Select VDDD
	AMUXBUSA			1	Select AMUXBUSA (VDDD branch)
	RESERVED			2	N/A
	VDDIO			3	N/A
	AMUXBUSB			4	Select AMUXBUSB (VDDD branch)
7	HVLVD1_EN	RW	RW	0	Enable HVLVD1 voltage monitor. HVLVD1 does not function during DEEPSLEEP, but it automatically returns to its configured setting after DEEPSLEEP wakeup. Do not change other HVLVD1 settings when enabled.

Bits	Name	SW	HW	Default or Enum	Description
8:12	HVLVD1_TRIPSEL_HT	RW	RW	0	Threshold selection for HVLVD1 for HT products. Detector accuracy is +/-4 percent of the nominal values listed below. Disable the detector (HVLVD1_EN=0) before changing the threshold. 0: rise 2.825V (nom), fall=2.8V (nom) 1: rise 2.925V (nom), fall=2.9V (nom) 2: rise 3.025V (nom), fall=3.0V (nom) 3: rise 3.125V (nom), fall=3.1V (nom) 4: rise 3.225V (nom), fall=3.2V (nom) 5: rise 3.325V (nom), fall=3.3V (nom) 6: rise 3.425V (nom), fall=3.4V (nom) 7: rise 3.525V (nom), fall=3.5V (nom) 8: rise 3.625V (nom), fall=3.6V (nom) 9: rise 3.725V (nom), fall=3.7V (nom) 10: rise 3.825V (nom), fall=3.8V (nom) 11: rise 3.925V (nom), fall=3.9V (nom) 12: rise 4.025V (nom), fall=4.0V (nom) 13: rise 4.125V (nom), fall=4.1V (nom) 14: rise 4.225V (nom), fall=4.2V (nom) 15: rise 4.325V (nom), fall=4.3V (nom) 16: rise 4.425V (nom), fall=4.4V (nom) 17: rise 4.525V (nom), fall=4.5V (nom) 18: rise 4.625V (nom), fall=4.6V (nom) 19: rise 4.725V (nom), fall=4.7V (nom) 20: rise 4.825V (nom), fall=4.8V (nom) 21: rise 4.925V (nom), fall=4.9V (nom) 22: rise 5.025V (nom), fall=5.0V (nom) 23: rise 5.125V (nom), fall=5.1V (nom) 24: rise 5.225V (nom), fall=5.2V (nom) 25: rise 5.325V (nom), fall=5.3V (nom) others: reserved
14	HVLVD1_DPSLP_EN_HT	RW	RW	0	Keep HVLVD1 voltage monitor enabled during DEEPSLEEP mode. This field is only used when HVLVD1_EN_HT==1.
15	HVLVD1_EN_HT	RW	RW	0	Enable HVLVD1 voltage monitor. This detector monitors vddd only. Do not change other HVLVD1 settings when enabled.
16:17	HVLVD1_EDGE_SEL	RW	RW	0	Sets which edge(s) will trigger an action when the threshold is crossed.
	DISABLE			0	Disabled
	RISING			1	Rising edge
	FALLING			2	Falling edge
	BOTH			3	Both rising and falling edges
18	HVLVD1_ACTION	RW	RW	0	Action taken when the threshold is crossed in the programmed direction(s)
	INTERRUPT			0	Generate an interrupt
	FAULT			1	Generate a fault

29.11.18 PWR_LVD_CTL2

Description: High Voltage / Low Voltage Detector (HVLVD) Configuration Register #2
Address: 0x40261024
Offset: 0x1024
Retention: Retained
IsDeepSleep: Yes
Comment: Trim and configuration bits for Voltage Monitoring System.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	HVLVD2_EN_HT [15:15]	HVLVD2_DPSLP_EN_HT [14:14]	None [13:13]	HVLVD2_TRIPSEL_HT [12:8]				

Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					HVLVD2_ACTION [18:18]	HVLVD2_EDGE_SEL [17:16]	

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
8:12	HVLVD2_TRIPSEL_HT	RW	RW	0	Threshold selection for HVLVD2 for HT products. Detector accuracy is +/-4 percent of the nominal values listed below. Disable the detector (HVLVD1_EN=0) before changing the threshold. 0: rise 2.825V (nom), fall=2.8V (nom) 1: rise 2.925V (nom), fall=2.9V (nom) 2: rise 3.025V (nom), fall=3.0V (nom) 3: rise 3.125V (nom), fall=3.1V (nom) 4: rise 3.225V (nom), fall=3.2V (nom) 5: rise 3.325V (nom), fall=3.3V (nom) 6: rise 3.425V (nom), fall=3.4V (nom) 7: rise 3.525V (nom), fall=3.5V (nom) 8: rise 3.625V (nom), fall=3.6V (nom) 9: rise 3.725V (nom), fall=3.7V (nom) 10: rise 3.825V (nom), fall=3.8V (nom) 11: rise 3.925V (nom), fall=3.9V (nom) 12: rise 4.025V (nom), fall=4.0V (nom) 13: rise 4.125V (nom), fall=4.1V (nom) 14: rise 4.225V (nom), fall=4.2V (nom) 15: rise 4.325V (nom), fall=4.3V (nom) 16: rise 4.425V (nom), fall=4.4V (nom) 17: rise 4.525V (nom), fall=4.5V (nom) 18: rise 4.625V (nom), fall=4.6V (nom) 19: rise 4.725V (nom), fall=4.7V (nom) 20: rise 4.825V (nom), fall=4.8V (nom) 21: rise 4.925V (nom), fall=4.9V (nom) 22: rise 5.025V (nom), fall=5.0V (nom) 23: rise 5.125V (nom), fall=5.1V (nom) 24: rise 5.225V (nom), fall=5.2V (nom) 25: rise 5.325V (nom), fall=5.3V (nom) others: reserved

Bits	Name	SW	HW	Default or Enum	Description
14	HVLVD2_DPSLP_EN_HT	RW	RW	0	Keep HVLVD2 voltage monitor enabled during DEEPSLEEP mode. This field is only used when HVLVD1_EN_HT==1.
15	HVLVD2_EN_HT	RW	RW	0	Enable HVLVD2 voltage monitor. This detector monitors vddd only. Do not change other HVLVD2 settings when enabled.
16:17	HVLVD2_EDGE_SEL	RW	RW	0	Sets which edge(s) will trigger an action when the threshold is crossed.
	DISABLE			0	Disabled
	RISING			1	Rising edge
	FALLING			2	Falling edge
	BOTH			3	Both rising and falling edges
18	HVLVD2_ACTION	RW	RW	0	Action taken when the threshold is crossed in the programmed direction(s)
	INTERRUPT			0	Generate an interrupt
	FAULT			1	Generate a fault

29.11.19 PWR_REGHC_CTL

Description: REGHC Control Register
Address: 0x40261028
Offset: 0x1028
Retention: Retained
IsDeepSleep: Yes
Comment: Control for the high-current regulator. This regulator requires external components. See datasheet. This register is only reset by HV resets (XRES, POR, BOD, OVD, OCD, HIBERNATE wakeup).
Default: 0x40000104

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name					REGHC_PMIC_DRV_VOUT [3:2]		None [1:1]	REGHC_MODE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	REGHC_PMIC_RADJ [14:12]			REGHC_PMIC_USE_RADJ [11:11]	REGHC_PMIC_USE_LINREG [10:10]	None [9:9]	REGHC_VADJ [8:8]

Bits	23	22	21	20	19	18	17	16
Name					REGHC_PMIC_STATUS_POLARITY [19:19]	REGHC_PMIC_STATUS_INEN [18:18]	REGHC_PMIC_CTL_POLARITY [17:17]	REGHC_PMIC_CTL_OUTEN [16:16]

Bits	31	30	29	28	27	26	25	24
Name	REGHC_CONFIGURED [31:31]	REGHC_TRANS_USE_OCD [30:30]	REGHC_PMIC_STATUS_WAIT [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	REGHC_MODE	RW	RW	0	REGHC control mode: 0: external transistor connected, 1: external PMIC connected
2:3	REGHC_PMIC_DRV_VOUT	RW	RW	1	Setting for DRV_VOUT pin for PMIC mode. See REGHC_VADJ for calculation of vadj. 2'b00: DRV_VOUT=vccd*0.9/vadj; 2'b01: DRV_VOUT=vccd*0.8/vadj; 2'b10: DRV_VOUT=vccd*0.6/vadj; 2'b11: DRV_VOUT=vccd

Bits	Name	SW	HW	Default or Enum	Description
4:8	REGHC_VADJ	RW	RW	16	Regulator output trim according to the formula $v_{adj} = (1.020V + REGHC\_VADJ \cdot 0.005V)$ plus an offset described below. For example, 0x1A => 1.15V (nominal). For transistor mode, REGHC will dynamically adjust DRV_VOUT so the supply targets the vadj voltage. Adjust for die to die variation by adding the signed offset value in SFLASH SRSS_PWR_OFFSET.REGHC_TRANS_VADJ_OFFSET. For PMIC mode, adjust for die to die variation by adding the signed offset value in SFLASH SRSS_PWR_OFFSET.PMIC_VADJ_OFFSET to the nominal calculated code. For PMIC mode, also see REGHC_PMIC_DRV_VOUT.
10	REGHC_PMIC_USE_LINREG	RW	RW	0	For REGHC external PMIC mode, controls whether hardware sequencer keeps the internal Active Linear Regulator enabled to improve supply supervision of vccd. When using this feature, if the PMIC fails to keep vccd above the internal regulator target, then the internal regulator will attempt to recover vccd. If the regulator current is too high, the regulator triggers an over-current detector (OCD) reset. 0: Internal Active Linear Regulator disabled after PMIC enabled. OCD is disabled.; 1: Internal Active Linear Regulator kept enabled. See datasheet for minimum PMIC vccd input to prevent OCD.
11	REGHC_PMIC_USE_RADJ	RW	RW	0	Controls whether hardware sequencer enables reset voltage adjustment circuit when enabling a PMIC.
12:14	REGHC_PMIC_RADJ	RW	RW	0	Reset voltage adjustment for PMIC as a factor (V_{fbk}/V_{ref}) where V_{fbk} is the feedback voltage and V_{ref} is the PMIC internal reference. The reset voltage adjustment circuit is enabled by the hardware sequencer if REGHC_PMIC_USE_RADJ=1. PMIC have V_{ref} of 0.8V or 0.9V, and the resulting reset voltage (V_{reset}) are precalculated in the table below: 3'b000: $V_{fbk}/V_{ref}=1.0000$, $V_{reset}=0.800V@ (V_{ref}=0.8V)$, $0.900V@ (V_{ref}=0.9V)$; 3'b001: $V_{fbk}/V_{ref}=1.0556$, $V_{reset}=0.844V@ (V_{ref}=0.8V)$, $0.950V@ (V_{ref}=0.9V)$; 3'b010: $V_{fbk}/V_{ref}=1.1111$, $V_{reset}=0.889V@ (V_{ref}=0.8V)$, $1.000V@ (V_{ref}=0.9V)$; 3'b011: $V_{fbk}/V_{ref}=1.1250$, $V_{reset}=0.900V@ (V_{ref}=0.8V)$, $1.013V@ (V_{ref}=0.9V)$; 3'b100: $V_{fbk}/V_{ref}=1.1667$, $V_{reset}=0.933V@ (V_{ref}=0.8V)$, $1.050V@ (V_{ref}=0.9V)$; 3'b101: $V_{fbk}/V_{ref}=1.1875$, $V_{reset}=0.950V@ (V_{ref}=0.8V)$, $1.069V@ (V_{ref}=0.9V)$; 3'b110: $V_{fbk}/V_{ref}=1.2500$, $V_{reset}=1.000V@ (V_{ref}=0.8V)$, $1.125V@ (V_{ref}=0.9V)$; 3'b111: $V_{fbk}/V_{ref}=1.3125$, $V_{reset}=1.050V@ (V_{ref}=0.8V)$, $1.181V@ (V_{ref}=0.9V)$;
16	REGHC_PMIC_CTL_OUTEN	RW	RW	0	Output enable for PMIC enable pin. Set this bit high to enable the driver on this pin.
17	REGHC_PMIC_CTL_POLARITY	RW	RW	0	Polarity used to enable the PMIC. The sequencer uses REGHC_PMIC_CTL_POLARITY to enable the PMIC, and it uses the complement to disable the PMIC.
18	REGHC_PMIC_STATUS_INEN	RW	RW	0	Input buffer enable for PMIC status input. Set this bit high to enable the input receiver.

Bits	Name	SW	HW	Default or Enum	Description
19	REGHC_PMIC_STATUS_POLARITY	RW	RW	0	The polarity used to trigger a reset action based on the PMIC status input. The reset system triggers a reset when the unmasked PMIC status matches this value.
20:29	REGHC_PMIC_STATUS_WAIT	RW	RW	0	Wait count in 4us steps after PMIC status ok. This is used by the hardware sequencer to allow additional settling time before disabling the internal regulator. The LSB is 32 IMO periods which results in a nominal LSB step of 4us.
30	REGHC_TRANS_USE_OCD	RW	RW	1	Reserved. Always write high.
31	REGHC_CONFIGURED	RW1S	RW1S	0	Indicates the REGHC has been configured. This is used to know if REGHC should be enabled in response to a debug power up request. It is recommended to not change REGHC settings after REGHC_CONFIGURED is set high, because it can cause failure if REGHC is enabled or transitioning.

29.11.20 PWR_REGHC_STATUS

Description: REGHC Status Register
Address: 0x4026102C
Offset: 0x102C
Retention: Retained
IsDeepSleep: Yes
Comment: Status register for REGHC.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					REGHC_CKT_OK [2:2]	REGHC_OCD_OK [1:1]	REGHC_ENABLED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			REGHC_PMIC_STATUS_OK [12:12]	None [11:10]		REGHC_OV_OUT [9:9]	REGHC_UV_OUT [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	REGHC_SEQ_BUSY [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	REGHC_ENABLED	R	R	0	Indicates the state of the REGHC enable/disable sequencer. This bit is only valid when REGHC_SEQ_BUSY==0. 0: REGHC sequencer indicates REGHC is disabled. 1: REGHC sequencer indicates REGHC is enabled.
1	REGHC_OCD_OK	R	R	0	Indicates the over-current detector is operating and the current drawn from REGHC is within limits. OCD is only a choice for transistor mode, and it is disabled for PMIC mode. 0: Current measurement exceeds limit or detector is OFF, 1: Current measurement within limit
2	REGHC_CKT_OK	R	R	0	Indicates the REGHC circuit is enabled and operating. It does not indicate that the voltage and current are within required limits for robust operation. 0: REGHC circuit is not ready. This can occur if the REGHC circuit is disabled or if it was recently enabled. 1: REGHC circuit is enabled and operating.
8	REGHC_UV_OUT	R	R	0	Reserved
9	REGHC_OV_OUT	R	R	0	Reserved
12	REGHC_PMIC_STATUS_OK	R	R	0	Indicates the PMIC status is ok. This includes polarity adjustment according to REGHC_PMIC_STATUS_POLARITY. 0: PMIC status is not ok or PMIC input buffer is disabled (REGHC_PMIC_STATUS_INEN==0); 1: PMIC status input buffer is enabled and indicates ok

Bits	Name	SW	HW	Default or Enum	Description
31	REGHC_SEQ_BUSY	R	R	0	Indicates the REGHC enable/disable sequencer is busy transitioning to/from REGHC. 0: Sequencer is not busy; 1: Sequencer is busy either enabling or disabling REGHC.

29.11.21 PWR_REGHC_CTL2

Description: REGHC Control Register 2
Address: 0x40261030
Offset: 0x1030
Retention: Retained
IsDeepSleep: Yes
Comment: Control for the high-current regulator. This regulator requires external components. See datasheet. This register is only reset by HV resets (XRES, POR, BOD, OVD, OCD, HIBERNATE wakeup).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REGHC_PMIC_STATUS_TIMEOUT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	REGHC_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	REGHC_PMIC_STATUS_TIMEOUT	RW	RW	0	Timeout while waiting for REGHC_PMIC_STATUS_OK==1 when switching to PMIC. 0: disables timeout. >0: enables timeout of REGHC_PMIC_STATUS_TIMEOUT*128us (nominal, clocked by IMO). Timeout expiration triggers reset.
31	REGHC_EN	RW	RW	0	Enable REGHC. This bit will not set if REGHC_CONFIGURED==0. Use PWR_REGHC_STATUS.ENABLED to know the actual status of REGHC. It will differ from this bit in the following cases: A) Do not enter DEEPSLEEP while the sequencer is busy (see PWR_REGHC_STATUS.REGHC_SEQ_BUSY). The hardware sequencer disables REGHC during DEEPSLEEP entry and enables it upon wakeup. B) The debugger requests the chip remain powered up. Hardware prevents REGHC from disabling when this bit is cleared. Hardware does not automatically enable REGHC in response to debugger power up request. If this bit is low when the debugger deasserts the power up request, the hardware sequencer will disable REGHC.

29.11.22 PWR_REGHC_CTL4

Description: REGHC Control Register 4
Address: 0x40261038
Offset: 0x1038
Retention: Retained
IsDeepSleep: Yes
Comment: Control for the high-current regulator. This regulator requires external components. See datasheet. This register is only reset by HV resets (XRES, POR, BOD, OVD, OCD, HIBERNATE wakeup). Do not change this register after setting PWR_REGHC_CTL.REGHC_CONFIGURED.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	REGHC_PMIC_DPSLP [31:31]	REGHC_PMIC_VADJ_DIS [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	REGHC_PMIC_VADJ_DIS	RW	RW	0	When operating in PMIC mode, disables the VADJ circuitry. This can be used to decrease current consumption if the entire feedback network is outside the device. 0: Device generates VADJ when PMIC is enabled. This allows the feedback loop to compensate for voltage drops in the PCB and package. 1: Device does not generate VADJ, and it must not be part of the PMIC feedback loop. This reduces current by turning off the internal resistor divider that generates VADJ. This setting is ineffective when REGHC_PMIC_RADJ_EN==1, and VADJ is generated in that case when PMIC is enabled.
31	REGHC_PMIC_DPSLP	RW	RW	0	When operating in PMIC mode, configures PMIC behavior during DEEPSLEEP. 0: Device operates from internal regulators during DEEPSLEEP. If PMIC is enabled at the beginning of the DEEPSLEEP transition, hardware changes to the internal regulators and disables the PMIC. 1: DEEPSLEEP transition does not change PMIC enable.

29.11.23 PWR_HIB_DATA

Description: HIBERNATE Data Register
Address: 0x40261040
Offset: 0x1040
Retention: Retained
IsDeepSleep: No
Comment: This register can retain information during HIBERNATE mode.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	HIB_DATA [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	HIB_DATA [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	HIB_DATA [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	HIB_DATA [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	HIB_DATA	RW	RW	0	Additional data that is retained through a HIBERNATE/WAKEUP sequence that can be used by firmware for any application-specific purpose. Note that waking up from HIBERNATE using XRES will reset this register.

29.11.24 CLK_PATH_SELECT

Description: Clock Path Select Register

Address: 0x40261200

Offset: 0x1200

Retention: Retained

IsDeepSleep: Yes

Comment: Selects a source for clock path. The output of this mux can be used as the root of a clock tree. If there is a PLL on the path, this mux output is the PLL reference clock. The related PLL register contains a mux to select whether the clock path uses the PLL output or is bypassed to the PLL reference clock.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					PATH_MUX [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	PATH_MUX	RW	RW	0	Selects a source for clock PATH<i>. Note that not all products support all clock sources. Selecting a clock source that is not supported will result in undefined behavior. It takes four cycles of the originally selected clock to switch away from it. Do not disable the original clock during this time.
	IMO			0	IMO - Internal R/C Oscillator
	EXTCLK			1	EXTCLK - External Clock Pin
	ECO			2	ECO - External-Crystal Oscillator
	ALTHF			3	ALTHF - Alternate High-Frequency clock input (product-specific clock)
	DSI_MUX			4	DSI_MUX - Output of DSI mux for this path. Using a DSI source directly as root of HFCLK will result in undefined behavior.
	LPECO			5	LPECO - Low-Power External-Crystal Oscillator

29.11.25 CLK_ROOT_SELECT

Description: Clock Root Select Register
Address: 0x40261240
Offset: 0x1240
Retention: Retained
IsDeepSleep: Yes
Comment: Selects a root for a HF clock tree and DSI input. There is a copy of this register for each clock root.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		ROOT_DIV [5:4]		ROOT_MUX [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							DIRECT_MUX [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	ROOT_MUX	RW	RW	0	Selects a clock path as the root of HFCLK<k> and for SRSS DSI input <k>. Use CLK_PATH_SELECT[i] to configure the desired path. Some paths may have FLL or PLL available (product-specific), and the control and bypass mux selections of these are in other registers. Configure the FLL using CLK_FLL_CONFIG register. Configure a PLL using the related CLK_PLL_CONFIG[k] register. Note that not all products support all clock sources. Selecting a clock source that is not supported will result in undefined behavior. It takes four cycles of the originally selected clock to switch away from it. Do not disable the original clock during this time.
	PATH0			0	Select PATH0 (can be configured for FLL)
	PATH1			1	Select PATH1 (can be configured for PLL0, if available in the product)
	PATH2			2	Select PATH2 (can be configured for PLL1, if available in the product)
	PATH3			3	Select PATH3 (can be configured for PLL2, if available in the product)
	PATH4			4	Select PATH4 (can be configured for PLL3, if available in the product)
	PATH5			5	Select PATH5 (can be configured for PLL4, if available in the product)
	PATH6			6	Select PATH6 (can be configured for PLL5, if available in the product)
	PATH7			7	Select PATH7 (can be configured for PLL6, if available in the product)
	PATH8			8	Select PATH8 (can be configured for PLL7, if available in the product)
	PATH9			9	Select PATH9 (can be configured for PLL8, if available in the product)

Bits	Name	SW	HW	Default or Enum	Description
	PATH10			10	Select PATH10 (can be configured for PLL9, if available in the product)
	PATH11			11	Select PATH11 (can be configured for PLL10, if available in the product)
	PATH12			12	Select PATH12 (can be configured for PLL11, if available in the product)
	PATH13			13	Select PATH13 (can be configured for PLL12, if available in the product)
	PATH14			14	Select PATH14 (can be configured for PLL13, if available in the product)
	PATH15			15	Select PATH15 (can be configured for PLL14, if available in the product)
4:5	ROOT_DIV	RW	RW	0	Selects predivider value for this clock root and DSI input. This divider is after DIRECT_MUX. For products with DSI, the output of this mux is routed to DSI for use as a signal. For products with clock supervision, the output of this mux is the monitored clock for CSV_HF<k>.
	NO_DIV			0	Transparent mode, feed through selected clock source w/o dividing.
	DIV_BY_2			1	Divide selected clock source by 2
	DIV_BY_4			2	Divide selected clock source by 4
	DIV_BY_8			3	Divide selected clock source by 8
8	DIRECT_MUX	RW	RW	MASK_DIRE CTMUX_DEF	Direct selection mux that allows IMO to bypass most of the clock mux structure. For products with multiple regulators, this mux can be used to reduce current without requiring significant reconfiguration of the clocking network. The default value of HFCLK<0>==ROOT_MUX, and the default value for other clock trees is product-specific.
	IMO			0	Select IMO
	ROOT_MUX			1	Select ROOT_MUX selection
31	ENABLE	RW	RW	0	Enable for this clock root. All clock roots default to disabled (ENABLE==0) except HFCLK0, which cannot be disabled.

29.11.26 CLK_SELECT

Description: Clock selection register
Address: 0x40261500
Offset: 0x1500
Retention: Retained
IsDeepSleep: Yes
Comment: Clock source selection register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					LFCLK_SEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	PUMP_ENABLE [15:15]	PUMP_DIV [14:12]			PUMP_SEL [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	LFCLK_SEL	RW	RW	0	Select source for LFCLK. Note that not all products support all clock sources. Selecting a clock source that is not supported will result in undefined behavior. Writes to this field are ignored unless the WDT is unlocked using WDT_LOCK register. It takes four cycles of the originally selected clock to switch away from it. Do not disable the original clock during this time.
	ILO0			0	ILO0 - Internal Low-speed Oscillator #0.
	WCO			1	WCO - Watch-Crystal Oscillator. Requires Backup domain to be present and properly configured (including external watch crystal, if used).
	ALTLF			2	ALTLF - Alternate Low-Frequency Clock. Capability is product-specific
	PILO			3	PILO - Precision ILO. If present, it works in DEEPSLEEP and higher modes. Does not work in HIBERNATE mode.
	ILO1			4	ILO1 - Internal Low-speed Oscillator #1, if present.
	ECO_PRESCALER			5	ECO_PRESCALER - External-Crystal Oscillator after prescaling, if present. Does not work in DEEPSLEEP or HIBERNATE modes. Intended for applications that operate in ACTIVE/SLEEP modes only. This option is only valid when ECO is present in the product.
	LPECO_PRESCALER			6	LPECO_PRESCALER - Low-Power External-Crystal Oscillator after prescaling, if present. This choice works in ACTIVE/SLEEP/DEEPSLEEP modes. This option is only valid when LPECO is present in the product.
8:11	PUMP_SEL	RW	RW	0	Reserved. Not used the product.
12:14	PUMP_DIV	RW	RW	0	Reserved. Not used in the product.
	NO_DIV			0	N/A
	DIV_BY_2			1	N/A

Bits	Name	SW	HW	Default or Enum	Description
	DIV_BY_4			2	N/A
	DIV_BY_8			3	N/A
	DIV_BY_16			4	N/A
15	PUMP_ENABLE	RW	RW	0	Reserved. Not used in the product.

29.11.27 CLK_TIMER_CTL

Description: Timer Clock Control Register
Address: 0x40261504
Offset: 0x1504
Retention: Retained
IsDeepSleep: Yes
Comment: Timer clock source selection register.
Default: 0x80070000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							TIMER_SEL [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						TIMER_HF0_DIV [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	TIMER_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TIMER_SEL	RW	RW	0	Obsolete. Do not use in new designs. Keep default value in new designs.
	IMO			0	Obsolete. Do not use in new designs. Keep default value in new designs.
	HF0_DIV			1	Obsolete. Do not use in new designs.
8:9	TIMER_HF0_DIV	RW	RW	0	Obsolete. Do not use in new designs. Keep default value in new designs.
	NO_DIV			0	Obsolete. Do not use in new designs. Keep default value in new designs.
	DIV_BY_2			1	Obsolete. Do not use in new designs.
	DIV_BY_4			2	Obsolete. Do not use in new designs.
	DIV_BY_8			3	Obsolete. Do not use in new designs.
16:23	TIMER_DIV	RW	RW	7	Obsolete. Do not use in new designs. Keep default value in new designs.
31	ENABLE	RW	RW	1	Obsolete. Do not use in new designs. Keep default value in new designs.

29.11.28 CLK_ILO0_CONFIG

Description: ILO0 Configuration

Address: 0x40261508

Offset: 0x1508

Retention: Retained

IsDeepSleep: No

Comment: Configuration register for ILO0. ILO0 configuration and trims are reset by XRES, HIBERNATE, and power-related resets, unless otherwise noted.

Default: 0x80000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ILO0_BACK UP [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	ILO0_MON_ENABLE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ILO0_BACKUP	RW	RW	0	This register indicates that ILO0 should stay enabled during XRES and HIBERNATE modes. If backup voltage domain is implemented on the product, this bit also indicates if ILO0 should stay enabled through power-related resets on other supplies, e.g.. BOD on VDDD/VCCD. Writes to this field are ignored unless the WDT is unlocked using WDT_LOCK register. This register is reset when the backup logic resets. 0: ILO0 turns off during XRES, HIBERNATE, and power-related resets. ILO0 configuration and trims are reset by these events. 1: ILO0 stays enabled, as described above. ILO0 configuration and trims are not reset by these events.
30	ILO0_MON_ENABLE	RW	RW	0	Reserved. Always write a zero. Writes to this field are ignored unless the WDT is unlocked using WDT_LOCK register.
31	ENABLE	RW	RW	1	Master enable for ILO. Writes to this field are ignored unless the WDT is unlocked using WDT_LOCK register. HT-variant: This register will not clear unless PWR_CTL2.BGREF_LPMODE==0. After enabling, the first ILO0 cycle occurs within 12us and is +/-10 percent accuracy. Thereafter, ILO0 is +/-5 percent accurate.

29.11.29 CLK_ILO1_CONFIG

Description: ILO1 Configuration
Address: 0x4026150C
Offset: 0x150C
Retention: Retained
IsDeepSleep: Yes
Comment: Configuration register for ILO1.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	ILO1_MON _ENABLE [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
30	ILO1_MON_ENABLE	RW	RW	0	Reserved. Always write a zero.
31	ENABLE	RW	RW	0	Master enable for ILO1. HT-variant: After enabling, the first ILO1 cycle occurs within 12us and is +/-10 percent accuracy. Thereafter, ILO1 is +/-5 percent accurate.

29.11.30 CLK_IMO_CONFIG

Description: IMO Configuration

Address: 0x40261518

Offset: 0x1518

Retention: Retained

IsDeepSleep: Yes

Comment: Internal high speed R/C oscillator configuration register. Note that this oscillator comes up active on power up. The oscillator provides the primary system clock (HFCLK) on power up until firmware configures differently. This oscillator is also used before system start to count out power up delays. This is done in fast IMO (FIMO) mode that does not require any external references and runs at a fixed 12MHz.

Default: 0x80000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
31	ENABLE	RW	RW	1	Master enable for IMO oscillator. This bit must be high at all times for all functions to work properly. Hardware will automatically disable the IMO during DEEPSLEEP, HIBERNATE, and XRES.

29.11.31 CLK_ECO_CONFIG

Description: ECO Configuration Register
Address: 0x4026151C
Offset: 0x151C
Retention: Retained
IsDeepSleep: Yes
Comment: Internal high speed oscillator configuration register for External-Crystal.
Default: 0x2

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						AGC_EN [1:1]	None [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ECO_EN [31:31]	None [30:29]		ECO_DIV_ENABLE [28:28]	ECO_DIV_DISABLE [27:27]	None [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
1	AGC_EN	RW	RW	1	Automatic Gain Control (AGC) enable. When set, the oscillation amplitude is controlled to the level selected by CLK_ECO_CONFIG2.ATRIM. When low, the amplitude is not explicitly controlled and can be as high as the vddd supply. WARNING: use care when disabling AGC because driving a crystal beyond its rated limit can permanently damage the crystal.
27	ECO_DIV_DISABLE	RW	RW	0	ECO prescaler disable command (mutually exclusive with ECO_DIV_ENABLE). SW sets this field to '1' and HW sets this field to '0'. HW sets ECO_DIV_DISABLE field to '0' immediately and HW sets CLK_ECO_PRESCALE.ECO_DIV_EN field to '0' immediately.
28	ECO_DIV_ENABLE	RW	RW	0	ECO prescaler enable command (mutually exclusive with ECO_DIV_DISABLE). ECO Prescaler only works in ACTIVE and SLEEP modes. SW sets this field to '1' to enable the divider and HW sets this field to '0' to indicate that divider enabling has completed. When the divider is enabled, its integer and fractional counters are initialized to '0'. If a divider is to be re-enabled using different integer and fractional divider values, the SW should follow these steps: 0: Disable the divider using the ECO_DIV_DISABLE field. 1: Configure CLK_ECO_PRESCALE registers. 2: Enable the divider using the ECO_DIV_ENABLE field. HW sets the ECO_DIV_ENABLE field to '0' when the enabling is performed and HW set CLK_ECO_PRESCALER.ENABLED to '1' when the enabling is performed.

Bits	Name	SW	HW	Default or Enum	Description
31	ECO_EN	RW	RW	0	Master enable for ECO oscillator. Configure the settings in CLK_ECO_CONFIG2 to work with the selected crystal, before enabling ECO.

29.11.32 CLK_ECO_PRESCALE

Description: ECO Prescaler Configuration Register
Address: 0x40261520
Offset: 0x1520
Retention: Retained
IsDeepSleep: Yes
Comment: Fractional prescaler value to bring down the ECO frequency to 32768 Hz if used as LFCLK.
 Do not change divider settings while ECO prescaler is enabled or enabling.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ECO_DIV_ENABLED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	ECO_FRAC_DIV [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	ECO_INT_DIV [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:26]						ECO_INT_DIV [25:24]	

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ECO_DIV_ENABLED	R	R	0	ECO prescaler enabled. HW sets this field to '1' as a result of an CLK_ECO_CONFIG.ECO_DIV_ENABLE command. HW sets this field to '0' as a result on a CLK_ECO_CONFIG.ECO_DIV_DISABLE command.
8:15	ECO_FRAC_DIV	RW	RW	0	8-bit fractional value, sufficient to get prescaler output within the +/-65ppm calibration range. Do not change this setting when ECO Prescaler is enabled.
16:25	ECO_INT_DIV	RW	RW	0	10-bit integer value allows for ECO frequencies up to 33.55MHz. Subtract one from the desired divide value when writing this field. For example, to divide by 1, write ECO_INT_DIV=0. Do not change this setting when ECO Prescaler is enabled.

29.11.33 CLK_ECO_STATUS

Description: ECO Status Register
Address: 0x40261524
Offset: 0x1524
Retention: Retained
IsDeepSleep: Yes
Comment: Status indications for external crystal oscillator (ECO).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						ECO_READY [1:1]	ECO_OK [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ECO_OK	R	R	0	Indicates the ECO internal oscillator circuit has sufficient amplitude. It may not meet the PPM accuracy or duty cycle spec.
1	ECO_READY	R	R	0	Indicates the ECO internal oscillator circuit has had enough time to fully stabilize. This is the output of a counter since ECO was enabled, and it does not check the ECO output. It is recommended to also confirm ECO_OK==1.

29.11.34 CLK_FLL_CONFIG

Description: FLL Configuration Register

Address: 0x40261530

Offset: 0x1530

Retention: Retained

IsDeepSleep: Yes

Comment: This register contains frequency lock loop (FLL) configuration. FLL circuit settings should not be changed while it is a selected clock (connected to logic). This prevents clock glitches that can crash the logic. Deselect the FLL using .BYPASS_SEL=FLL_REF

Default: 0x1000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FLL_MULT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	FLL_MULT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:18]						FLL_MULT [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	FLL_ENABLE [31:31]	None [30:25]						FLL_OUTPUT_DIV [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:17	FLL_MULT	RW	RW	0	Multiplier to determine CCO frequency in multiples of the frequency of the selected reference clock (Fref). $F_{ll} = (FLL\_MULT) * (Fref / REFERENCE\_DIV) / (OUTPUT\_DIV + 1)$
24	FLL_OUTPUT_DIV	RW	RW	1	Control bits for Output divider. Set the divide value before enabling the FLL, and do not change it while FLL is enabled. 0: no division 1: divide by 2

Bits	Name	SW	HW	Default or Enum	Description
31	FLL_ENABLE	RW	RW	0	Master enable for FLL. The FLL requires firmware sequencing when enabling and disabling. Hardware handles sequencing automatically when entering/exiting DEEPSLEEP. To enable the FLL, use the following sequence: 1) Configure FLL and CCO settings. Do not modify CLK_FLL_CONFIG3.BYPASS_SEL (must be AUTO) or CLK_FLL_CONFIG.FLL_ENABLE (must be 0). 2) Enable the CCO by writing CLK_FLL_CONFIG4.CCO_ENABLE=1 3) Wait until CLK_FLL_STATUS.CCO_READY==1. 4) Ensure the reference clock has stabilized. 5) Write FLL_ENABLE=1. 6) Optionally wait until CLK_FLL_STATUS.LOCKED==1. The hardware automatically changes to the FLL output when LOCKED==1. To disable the FLL, use the following sequence: 1) Write CLK_FLL_CONFIG3.BYPASS_SEL=FLL_REF. 2) Read CLK_FLL_CONFIG3.BYPASS_SEL to ensure the write completes (read is not optional). 3) Wait at least ten cycles of either FLL reference clock or FLL output clock, whichever is slower. 4) Disable FLL with FLL_ENABLE=0. 5) Disable the CCO by writing CLK_FLL_CONFIG4.CCO_ENABLE=0. 6) Write CLK_FLL_CONFIG3.BYPASS_SEL=AUTO. 7) Read CLK_FLL_CONFIG3.BYPASS_SEL to ensure the write completes (read is not optional). 8) Wait three cycles of FLL reference clock. 0: Block is powered off 1: Block is powered on

29.11.35 CLK_FLL_CONFIG2

Description: FLL Configuration Register 2

Address: 0x40261534

Offset: 0x1534

Retention: Retained

IsDeepSleep: Yes

Comment: This register contains frequency lock loop (FLL) configuration. FLL circuit settings should not be changed while it is a selected clock (connected to logic). This prevents clock glitches that can crash the logic. Deselect the FLL using .BYPASS_SEL=FLL_REF

Default: 0x20001

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FLL_REF_DIV [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			FLL_REF_DIV [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	LOCK_TOL [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	UPDATE_TOL [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:12	FLL_REF_DIV	RW	RW	1	Control bits for reference divider. Set the divide value before enabling the FLL, and do not change it while FLL is enabled. 0: illegal (undefined behavior) 1: divide by 1 ... 8191: divide by 8191
16:23	LOCK_TOL	RW	RW	2	Lock tolerance sets the error threshold for when the FLL output is considered locked to the reference input. A high tolerance can be used to lock more quickly or allow less accuracy. The tolerance is the allowed difference between the count value for the ideal formula and the measured value. 0: tolerate error of 1 count value 1: tolerate error of 2 count values ... 255: tolerate error of 256 count values
24:31	UPDATE_TOL	RW	RW	0	Update tolerance sets the error threshold for when the FLL will update the CCO frequency settings. The update tolerance is the allowed difference between the count value for the ideal formula and the measured value. UPDATE_TOL should be less than LOCK_TOL.

29.11.36 CLK_FLL_CONFIG3

Description: FLL Configuration Register 3

Address: 0x40261538

Offset: 0x1538

Retention: Retained

IsDeepSleep: Yes

Comment: This register contains frequency lock loop (FLL) configuration. Do not change settings while the FLL is running, except BYPASS_SEL.

Default: 0x2800

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FLL_LF_PGAIN [7:4]				FLL_LF_IGAIN [3:0]			
Bits	15	14	13	12	11	10	9	8
Name	SETTLING_COUNT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:21]				SETTLING_COUNT [20:16]			
Bits	31	30	29	28	27	26	25	24
Name	None [31:30]		BYPASS_SEL [29:28]		None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	FLL_LF_IGAIN	RW	RW	0	FLL Loop Filter Gain Setting #1. The proportional gain is the sum of FLL_LF_IGAIN and FLL_LF_PGAIN. 0: 1/256 1: 1/128 2: 1/64 3: 1/32 4: 1/16 5: 1/8 6: 1/4 7: 1/2 8: 1.0 9: 2.0 10: 4.0 11: 8.0 >=12: illegal
4:7	FLL_LF_PGAIN	RW	RW	0	FLL Loop Filter Gain Setting #2. The proportional gain is the sum of FLL_LF_IGAIN and FLL_LF_PGAIN. 0: 1/256 1: 1/128 2: 1/64 3: 1/32 4: 1/16 5: 1/8 6: 1/4 7: 1/2 8: 1.0 9: 2.0 10: 4.0 11: 8.0 >=12: illegal

Bits	Name	SW	HW	Default or Enum	Description
8:20	SETTLING_COUNT	RW	RW	40	Number of undivided reference clock cycles to wait after changing the CCO trim until the loop measurement restarts. A delay allows the CCO output to settle and gives a more accurate measurement. The default is tuned to an 8MHz reference clock since the IMO is expected to be the most common use case. 0: no settling time 1: wait one reference clock cycle ... 8191: wait 8191 reference clock cycles
28:29	BYPASS_SEL	RW	RW	0	Bypass mux located just after FLL output. This register can be written while the FLL is enabled. When changing BYPASS_SEL, do not turn off the reference clock or CCO clock for five cycles (whichever is slower). Whenever BYPASS_SEL is changed, it is required to read CLK_FLL_CONFIG3 to ensure the change takes effect.
	AUTO			0	Automatic using lock indicator. When unlocked, automatically selects FLL reference input (bypass mode). When locked, automatically selects FLL output. This can allow some processing to occur while the FLL is locking, such as after DEEPSLEEP wakeup. It is incompatible with clock supervision, because the frequency changes based on the lock signal.
	LOCKED_OR_NOTHING			1	Similar to AUTO, except the clock is gated off when unlocked. This is compatible with clock supervision, because the supervisors allow no clock during startup (until a timeout occurs), and the clock targets the proper frequency whenever it is running.
	FLL_REF			2	Select FLL reference input (bypass mode). Ignores lock indicator
	FLL_OUT			3	Select FLL output. Ignores lock indicator.

29.11.37 CLK_FLL_CONFIG4

Description: FLL Configuration Register 4

Address: 0x4026153C

Offset: 0x153C

Retention: Retained

IsDeepSleep: Yes

Comment: This register contains frequency lock loop (FLL) configuration. Do not change settings while the FLL is running.

Default: 0xFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CCO_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:11]					CCO_RANGE [10:8]		
Bits	23	22	21	20	19	18	17	16
Name	CCO_FREQ [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CCO_ENABLE [31:31]	CCO_HW_UPDATE_DIS [30:30]	None [29:25]					CCO_FREQ [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CCO_LIMIT	RW	RW	255	Maximum CCO offset allowed (used to prevent FLL dynamics from selecting an CCO frequency that the logic cannot support)
8:10	CCO_RANGE	RW	RW	0	Frequency range of CCO
	RANGE0			0	Target frequency is in range [48, 64) MHz
	RANGE1			1	Target frequency is in range [64, 85) MHz
	RANGE2			2	Target frequency is in range [85, 113) MHz
	RANGE3			3	Target frequency is in range [113, 150) MHz
	RANGE4			4	Target frequency is in range [150, 200] MHz
16:24	CCO_FREQ	RW	RW	0	CCO frequency code. This is updated by HW when the FLL is enabled. It can be manually updated to use the CCO in an open loop configuration. The meaning of each frequency code depends on the range.
30	CCO_HW_UPDATE_DIS	RW	RW	0	Disable CCO frequency update by FLL hardware 0: Hardware update of CCO settings is allowed. Use this setting for normal FLL operation. 1: Hardware update of CCO settings is disabled. Use this setting for open-loop FLL operation.
31	CCO_ENABLE	RW	RW	0	Enable the CCO. It is required to enable the CCO before using the FLL. 0: Block is powered off 1: Block is powered on

29.11.38 CLK_FLL_STATUS

Description: FLL Status Register

Address: 0x40261540

Offset: 0x1540

Retention: Retained

IsDeepSleep: No

Comment: This register indicates status for the FLL. This register is synchronized during an AHB read transaction. This causes a number wait-states to be inserted in the transaction depending on the frequency ratio between system and FLL frequency.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CCO_READY [2:2]	UNLOCK_OC CURRED [1:1]	LOCKED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOCKED	R	R	0	FLL Lock Indicator
1	UNLOCK_OCCURRED	RW1C	RW1C	0	This bit sets whenever the FLL is enabled and goes out of lock. This bit stays set until cleared by firmware.
2	CCO_READY	R	R	0	This indicates that the CCO is internally settled and ready to use.

29.11.39 CLK_ECO_CONFIG2

Description: ECO Configuration Register 2
Address: 0x40261544
Offset: 0x1544
Retention: Retained
IsDeepSleep: Yes
Comment: Internal high speed oscillator configuration register for External-Crystal.
Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	ATRIM [7:4]				None [3:3]	WDTRIM [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:15]	GTRIM [14:12]			RTRIM [11:10]		FTRIM [9:8]	

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	WDTRIM	RW	RW	3	Watch Dog Trim. Sets the minimum oscillation amplitude (Vp) for the crystal drive level. The minimum amplitude detector output is readable in CLK_ECO_STATUS.ECO_OK. 0x0: Vp > 0.05V 0x1: Vp > 0.10V 0x2: Vp > 0.15V 0x3: Vp > 0.20V 0x4: Vp > 0.25V 0x5: Vp > 0.30V 0x6: Vp > 0.35V 0x7: Vp > 0.40V

Bits	Name	SW	HW	Default or Enum	Description
4:7	ATRIM	RW	RW	0	Amplitude trim. Sets maximum oscillation amplitude (Vp) to set the crystal drive level when ECO_CONFIG.AGC_EN=1. When AGC_EN=0, most values of this register are unused, except as noted. WARNING: use care when setting this field because driving a crystal beyond its rated limit can permanently damage the crystal. 0x0: Vp < 0.35V 0x1: Vp < 0.40V 0x2: Vp < 0.45V 0x3: Vp < 0.50V 0x4: Vp < 0.55V 0x5: Vp < 0.60V 0x6: Vp < 0.65V 0x7: Vp < 0.70V 0x8: Vp < 0.75V 0x9: Vp < 0.80V 0xA: Vp < 0.85V 0xB: Vp < 0.90V 0xC: Vp < 0.95V 0xD: Vp < 1.00V 0xE: Vp < 1.05V 0xF: Vp < 1.10V when AGC_EN=1. When AGC_EN=0, this setting enables maximum swing between vddd and vssd.
8:9	FTRIM	RW	RW	0	Filter Trim - 3rd harmonic oscillation
10:11	RTRIM	RW	RW	0	Feedback resistor Trim
12:14	GTRIM	RW	RW	0	Gain Trim - Startup time.

29.11.40 CLK_PLL_CONFIG

Description: PLL Configuration Register

Address: 0x40261600

Offset: 0x1600

Retention: Retained

IsDeepSleep: Yes

Comment: This register contains PLL configuration. There is a copy of this register for each PLL. PLL circuit settings should not be changed while it is a selected clock (connected to logic). This prevents clock glitches that can crash the logic.

Default: 0x20116

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	FEEDBACK_DIV [6:0]						
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			REFERENCE_DIV [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			OUTPUT_DIV [20:16]				
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:30]	BYPASS_SEL [29:28]		PLL_LF_MODE [27:27]	LOCK_DELAY [26:25]		None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:6	FEEDBACK_DIV	RW	RW	22	Control bits for feedback divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0-21: illegal (undefined behavior) 22: divide by 22 ... 112: divide by 112 >112: illegal (undefined behavior)
8:12	REFERENCE_DIV	RW	RW	1	Control bits for reference divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0: illegal (undefined behavior) 1: divide by 1 ... 20: divide by 20 others: illegal (undefined behavior)
16:20	OUTPUT_DIV	RW	RW	2	Control bits for Output divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0: illegal (undefined behavior) 1: illegal (undefined behavior) 2: divide by 2. Suitable for direct usage as HFCLK source. ... 16: divide by 16. Suitable for direct usage as HFCLK source. >16: illegal (undefined behavior)

Bits	Name	SW	HW	Default or Enum	Description
25:26	LOCK_DELAY	RW	RW	0	Configures the sensitivity of the lock detection logic. 0: normal operation 1: reduced sensitivity to allow tracking a modulating reference clock. When this option is selected, configure fVCO=320MHz. The PLL can track the a reference clock frequency that modulates within +/-4 percent at a rate of fREF/1000 MHz. 2,3: reserved (do not use)
27	PLL_LF_MODE	RW	RW	0	VCO frequency range selection. Configure this bit according to the targeted VCO frequency. Do not change this setting while the PLL is enabled. 0: VCO frequency is [200MHz, 400MHz] 1: VCO frequency is [170MHz, 200MHz]
28:29	BYPASS_SEL	RW	RW	0	Bypass mux located just after PLL output. This selection is glitch-free and can be changed while the PLL is running. When changing BYPASS_SEL, do not turn off the reference clock or PLL clock for five cycles (whichever is slower).
	AUTO			0	Automatic using lock indicator. When unlocked, automatically selects PLL reference input (bypass mode). When locked, automatically selects PLL output. If ENABLE=0, automatically selects PLL reference input.
	LOCKED_OR_NOTHING			1	Similar to AUTO, except the clock is gated off when unlocked. This is compatible with clock supervision, because the supervisors allow no clock during startup (until a timeout occurs), and the clock targets the proper frequency whenever it is running. If ENABLE=0, no clock is output.
	PLL_REF			2	Select PLL reference input (bypass mode). Ignores lock indicator
	PLL_OUT			3	Select PLL output. Ignores lock indicator. If ENABLE=0, no clock is output.
31	ENABLE	RW	RW	0	Master enable for PLL. Setup FEEDBACK_DIV, REFERENCE_DIV, and OUTPUT_DIV at least one cycle before setting ENABLE=1. $F_{pll} = (FEEDBACK\_DIV) * (F_{ref} / REFERENCE\_DIV) / (OUTPUT\_DIV)$ 0: Block is disabled. When the PLL disables, hardware controls the bypass mux as described in BYPASS_SEL, before disabling the PLL circuit. 1: Block is enabled

29.11.41 CLK_PLL_STATUS

Description: PLL Status Register

Address: 0x40261640

Offset: 0x1640

Retention: Retained

IsDeepSleep: No

Comment: This register indicates status for the PLL. There is a copy of this register for each PLL. This register is synchronized during an AHB read transaction. This causes a number wait-states to be inserted in the transaction depending on the frequency ration between system and PLL frequency.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						UNLOCK_OC CURRED [1:1]	LOCKED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOCKED	R	R	0	PLL Lock Indicator
1	UNLOCK_OCCURRED	RW1C	RW1C	0	This bit sets whenever the PLL Lock bit goes low, and stays set until cleared by firmware.

29.11.42 CSV_REF_SEL

Description: Select CSV Reference clock for Active domain
Address: 0x40261700
Offset: 0x1700
Retention: Retained
IsDeepSleep: Yes
Comment: Selects a source to be used as the Reference clock for CSV in the Active domain. (matching CLK_PATH_SELECT.PATH_MUX)
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					REF_MUX [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	REF_MUX	RW	RW	0	Selects a source for clock clk_ref_hf. Note that not all products support all clock sources. Selecting a clock source that is not supported will result in undefined behavior. It takes four cycles of the originally selected clock to switch away from it. Do not disable the original clock during this time.
	IMO			0	IMO - Internal R/C Oscillator
	EXTCLK			1	EXTCLK - External Clock Pin
	ECO			2	ECO - External-Crystal Oscillator
	ALTHF			3	ALTHF - Alternate High-Frequency clock input (product-specific clock)

29.11.43 RES_CAUSE

Description: Reset Cause Observation Register

Address: 0x40261800

Offset: 0x1800

Retention: Retained

IsDeepSleep: Yes

Comment: Indicates the cause for reset(s) that occurred in the system. All bits in this register assert when the corresponding reset cause occurs and must be cleared by firmware. Low-voltage cause bits are reset whenever the low-voltage supply is initialized, including XRES, POR, brown-out, and during Hibernate wakeup. HT products also clear low-voltage cause bits for over-voltage, over-current, and WDT resets. Refer to the reset source documentation to understand what reset source behavior for different configuration or modes.

Default: 0x40000000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESET_MCWDT2 [7:7]	RESET_MCWDT1 [6:6]	RESET_MCWDT0 [5:5]	RESET_SOFT [4:4]	RESET_TC DBGRESET [3:3]	RESET_DPSLP_FAULT [2:2]	RESET_ACT_FAULT [1:1]	RESET_WDT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:9]							RESET_MCWDT3 [8:8]

Bits	23	22	21	20	19	18	17	16
Name	RESET_OCD_ACT_LINREG [23:23]	RESET_OVD_VCCD [22:22]	RESET_OVD_VDDA [21:21]	RESET_OVD_VDDD [20:20]	RESET_BOD_VCCD [19:19]	RESET_BOD_VDDA [18:18]	RESET_BOD_VDDD [17:17]	RESET_XRES [16:16]

Bits	31	30	29	28	27	26	25	24
Name	None [31:31]	RESET_POR_VDDD [30:30]	RESET_STRUCT_XRES [29:29]	RESET_PXRES [28:28]	None [27:27]	RESET_PMIC [26:26]	RESET_OCD_REGHC [25:25]	RESET_OCD_DPSLP_LINREG [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	RESET_WDT	RW1C	RW1C	0	A basic WatchDog Timer (WDT) reset has occurred since last power cycle. ULP products: This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above). For products that support high-voltage cause detection, this bit blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR. This bit is not blocked by other HV cause bits.
1	RESET_ACT_FAULT	RW1C	RW1C	0	Fault logging system requested a reset from its Active logic. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
2	RESET_DPSLP_FAULT	RW1C	RW1C	0	Fault logging system requested a reset from its DeepSleep logic. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).

Bits	Name	SW	HW	Default or Enum	Description
3	RESET_TC_DBGRESET	RW1C	RW1C	0	Test controller or debugger asserted reset. Only resets debug domain. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
4	RESET_SOFT	RW1C	RW1C	0	A CPU requested a system reset through it's SYSRESETREQ. This can be done via a debugger probe or in firmware. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
5	RESET_MCWDT0	RW1C	RW1C	0	Multi-Counter Watchdog timer reset #0. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
6	RESET_MCWDT1	RW1C	RW1C	0	Multi-Counter Watchdog timer reset #1. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
7	RESET_MCWDT2	RW1C	RW1C	0	Multi-Counter Watchdog timer reset #2. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
8	RESET_MCWDT3	RW1C	RW1C	0	Multi-Counter Watchdog timer reset #3. This is a low-voltage cause bit that hardware clears when the low-voltage supply is initialized (see comments above).
16	RESET_XRES	RW1C	RW1C	0	External XRES pin was asserted. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR. This bit is not blocked by other HV cause bits.
17	RESET_BODVDDD	RW1C	RW1C	0	External VDDD supply crossed brown-out limit. Note that this cause will only be observable as long as the VDDD supply does not go below the POR (power on reset) detection limit. Below this limit it is not possible to reliably retain information in the device. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
18	RESET_BODVDDA	RW1C	RW1C	0	External VDDA supply crossed the brown-out limit. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
19	RESET_BODVCCD	RW1C	RW1C	0	Internal VCCD core supply crossed the brown-out limit. Note that this detector will detect gross issues with the internal core supply, but may not catch all brown-out conditions. Functional and timing supervision (CSV, WDT) is provided to create fully failsafe internal crash detection. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
20	RESET_OVDVDDD	RW1C	RW1C	0	Overvoltage detection on the external VDDD supply. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
21	RESET_OVDVDDA	RW1C	RW1C	0	Overvoltage detection on the external VDDA supply. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.

Bits	Name	SW	HW	Default or Enum	Description
22	RESET_OVDVCCD	RW1C	RW1C	0	Overvoltage detection on the internal core VCCD supply. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
23	RESET_OCD_ACT_LINREG	RW1C	RW1C	0	Overcurrent detection on the internal VCCD supply when supplied by the ACTIVE power mode linear regulator. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
24	RESET_OCD_DPSLP_LINREG	RW1C	RW1C	0	Overcurrent detection on the internal VCCD supply when supplied by the DEEPSLEEP power mode linear regulator. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
25	RESET_OCD_REGHC	RW1C	RW1C	0	Overcurrent detection from REGHC (if present). If REGHC is not present, hardware will never set this bit. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
26	RESET_PMIC	RW1C	RW1C	0	PMIC status triggered a reset. If PMIC control is not present, hardware will never set this bit. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR.
28	RESET_PXRES	RW1C	RW1C	0	PXRES triggered. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR. This bit is not blocked by other HV cause bits.
29	RESET_STRUCT_XRES	RW1C	RW1C	0	Structural reset was asserted. This is a high-voltage cause bit that blocks recording of other high-voltage cause bits, except RESET_PORVDDD. Hardware clears this bit during POR. This bit is not blocked by other HV cause bits.
30	RESET_PORVDDD	RW1C	RW1C	1	Indicator that a POR occurred. This is a high-voltage cause bit, and hardware clears the other bits when this one is set. It does not block further recording of other high-voltage causes.

29.11.44 RES_CAUSE2

Description: Reset Cause Observation Register 2
Address: 0x40261804
Offset: 0x1804
Retention: Retained
IsDeepSleep: Yes
Comment: Indicates the cause for the latest reset(s) that occurred in the system. Note that resets due to power up and brown-outs below state retention voltages in regulated and unregulated domains cannot be distinguished from each other. All bits in this register assert when the corresponding reset cause occurs and must be cleared by firmware. These bits are cleared by hardware only during XRES, POR or after a detected brown-out.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	RESET_CSV_HF [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	RESET_CSV_HF [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:17]							RESET_CSV_REF [16:16]
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	RESET_CSV_HF	RW1C	RW1C	0	Clock supervision logic requested a reset due to loss or frequency violation of a high-frequency clock. Each bit index K corresponds to a HFCLK<K>. Unimplemented clock bits return zero.
16	RESET_CSV_REF	RW1C	RW1C	0	Clock supervision logic requested a reset due to loss or frequency violation of the reference clock source that is used to monitor the other HF clock sources.

29.11.45 CLK_TRIM_ILO0_CTL

Description: ILO0 Trim Register

Address: 0x40263014

Offset: 0x3014

Retention: Retained

IsDeepSleep: No

Comment: Trims ILO frequency. Determined during manufacturing sort/class, but may be updated in the field to calibrate voltage and temperature conditions. This register is protected by WDT_CTL.WDT_LOCK. ILO0 configuration and trims are reset by XRES and power-related resets, unless configured otherwise.

Default: 0x52C

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		ILO0_FTRIM [5:0]					

Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				ILO0_MONTRIM [11:8]			

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	ILO0_FTRIM	RW	RW	44	ILO0 frequency trims. LSB step size is 1.5 percent (typical) of the frequency.
8:11	ILO0_MONTRIM	RW	RW	5	ILO0 internal monitor trim.

29.11.46 CLK_TRIM_ILO1_CTL

Description: ILO1 Trim Register
Address: 0x40263220
Offset: 0x3220
Retention: Retained
IsDeepSleep: Yes
Comment: Trims ILO frequency. Determined during manufacturing sort/class, but may be updated in the field to calibrate voltage and temperature conditions.
Default: 0x52C

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		ILO1_FTRIM [5:0]					
Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				ILO1_MONTRIM [11:8]			
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:5	ILO1_FTRIM	RW	RW	44	ILO1 frequency trims. LSB step size is 1.5 percent (typical) of the frequency.
8:11	ILO1_MONTRIM	RW	RW	5	ILO1 internal monitor trim.

29.11.47 CSV_HF

29.11.47.1 CSV

29.11.47.1.1 CSV_HF_CSV_REF_CTL

Description: Clock Supervision Reference Control
Address: 0x40261400
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Controls clock supervision for a clock tree.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STARTUP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	STARTUP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CSV_EN [31:31]	CSV_ACTION [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	STARTUP	RW	RW	0	Startup delay time -1 (in reference clock cycles), after enable or DeepSleep wakeup, from reference clock start to monitored clock start. At a minimum (both clocks running): $STARTUP \geq (PERIOD + 3) * FREQ\_RATIO - UPPER$, with $FREQ\_RATIO = (Reference\ frequency / Monitored\ frequency)$ On top of that the actual clock startup delay and the margin for accuracy of both clocks must be added.
30	CSV_ACTION	RW	RW	0	Specifies the action taken when an anomaly is detected on the monitored clock. CSV in DeepSleep domain always do a Fault report (which also wakes up the system).
	FAULT			0	Do a Fault report.
	RESET			1	Cause a power reset. This should only be used for clk_hf0.
31	CSV_EN	RW	RW	0	Enables clock supervision, both frequency and loss. CSV in Active domain: Clock supervision is reset during DeepSleep and Hibernate modes. When enabled it begins operating automatically after a DeepSleep wakeup, but it must be reconfigured after Hibernate wakeup. CSV in DeepSleep domain: Clock supervision is reset during Hibernate mode. It must be reconfigured after Hibernate wakeup. A CSV error detection is reported to the Fault structure, or instead it can generate a power reset.

29.11.47.1.2 CSV_HF_CSV_REF_LIMIT

Description: Clock Supervision Reference Limits
Address: 0x40261404
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LOWER [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	UPPER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	UPPER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	LOWER	RW	RW	0	Cycle time lower limit. Set the lower limit -1, in reference clock cycles, before the next monitored clock event is allowed to happen. If a monitored clock event happens before this limit is reached a CSV error is detected. LOWER must be at least 1 less than UPPER. In case the clocks are asynchronous LOWER must be at least 3 less than UPPER.
16:31	UPPER	RW	RW	0	Cycle time upper limit. Set the upper limit -1, in reference clock cycles, before (or same time) the next monitored clock event must happen. If a monitored clock event does not happen before this limit is reached, or does not happen at all (clock loss), a CSV error is detected.

29.11.47.1.3 CSV_HF_CSV_MON_CTL

Description: Clock Supervision Monitor Control
Address: 0x40261408
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	PERIOD	RW	RW	0	Period time. Set the Period -1, in monitored clock cycles, before the next monitored clock event happens. $PERIOD \leq (UPPER+1) / FREQ\_RATIO - 1$, with $FREQ\_RATIO = (\text{Reference frequency} / \text{Monitored frequency})$ In case the clocks are asynchronous: $PERIOD \leq UPPER / FREQ\_RATIO - 1$ Additionally margin must be added for accuracy of both clocks.

29.11.48 CSV_REF

29.11.48.1 CSV

29.11.48.1.1 CSV_REF_CSV_REF_CTL

Description: Clock Supervision Reference Control
Address: 0x40261710
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Controls clock supervision for a clock tree.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STARTUP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	STARTUP [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CSV_EN [31:31]	CSV_ACTION [30:30]	None [29:24]					

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	STARTUP	RW	RW	0	Startup delay time -1 (in reference clock cycles), after enable or DeepSleep wakeup, from reference clock start to monitored clock start. At a minimum (both clocks running): $STARTUP \geq (PERIOD + 3) * FREQ\_RATIO - UPPER$, with $FREQ\_RATIO = (Reference\ frequency / Monitored\ frequency)$ On top of that the actual clock startup delay and the margin for accuracy of both clocks must be added.
30	CSV_ACTION	RW	RW	0	Specifies the action taken when an anomaly is detected on the monitored clock. CSV in DeepSleep domain always do a Fault report (which also wakes up the system).
	FAULT			0	Do a Fault report.
	RESET			1	Cause a power reset. This should only be used for clk_hf0.
31	CSV_EN	RW	RW	0	Enables clock supervision, both frequency and loss. CSV in Active domain: Clock supervision is reset during DeepSleep and Hibernate modes. When enabled it begins operating automatically after a DeepSleep wakeup, but it must be reconfigured after Hibernate wakeup. CSV in DeepSleep domain: Clock supervision is reset during Hibernate mode. It must be reconfigured after Hibernate wakeup. A CSV error detection is reported to the Fault structure, or instead it can generate a power reset.

29.11.48.1.2 CSV_REF_CSV_REF_LIMIT

Description: Clock Supervision Reference Limits
Address: 0x40261714
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LOWER [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	UPPER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	UPPER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	LOWER	RW	RW	0	Cycle time lower limit. Set the lower limit -1, in reference clock cycles, before the next monitored clock event is allowed to happen. If a monitored clock event happens before this limit is reached a CSV error is detected. LOWER must be at least 1 less than UPPER. In case the clocks are asynchronous LOWER must be at least 3 less than UPPER.
16:31	UPPER	RW	RW	0	Cycle time upper limit. Set the upper limit -1, in reference clock cycles, before (or same time) the next monitored clock event must happen. If a monitored clock event does not happen before this limit is reached, or does not happen at all (clock loss), a CSV error is detected.

29.11.48.1.3 CSV_REF_CSV_MON_CTL

Description: Clock Supervision Monitor Control
Address: 0x40261718
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	PERIOD	RW	RW	0	Period time. Set the Period -1, in monitored clock cycles, before the next monitored clock event happens. $PERIOD \leq (UPPER+1) / FREQ\_RATIO - 1$, with $FREQ\_RATIO = (\text{Reference frequency} / \text{Monitored frequency})$ In case the clocks are asynchronous: $PERIOD \leq UPPER / FREQ\_RATIO - 1$ Additionally margin must be added for accuracy of both clocks.

29.11.49 CSV_LF

29.11.49.1 CSV

29.11.49.1.1 CSV_LF_CSV_REF_CTL

Description: Clock Supervision Reference Control
Address: 0x40261720
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Controls clock supervision for a clock tree.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STARTUP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CSV_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	STARTUP	RW	RW	0	Startup delay time -1 (in reference clock cycles), after enable, from reference clock start to monitored clock start. At a minimum (both clocks running): $STARTUP \geq (PERIOD + 3) * FREQ\_RATIO - UPPER$, with $FREQ\_RATIO = (Reference\ frequency / Monitored\ frequency)$ On top of that the actual clock startup delay and the margin for accuracy of both clocks must be added.
31	CSV_EN	RW	RW	0	Enables clock supervision, both frequency and loss. CSV in Active domain: Clock supervision is reset during DeepSleep and Hibernate modes. When enabled it begins operating automatically after a DeepSleep wakeup, but it must be reconfigured after Hibernate wakeup. CSV in DeepSleep domain: Clock supervision is reset during Hibernate mode. It must be reconfigured after Hibernate wakeup. CSV in Backup domain: Clock supervision operates during Hibernate mode, can be configured to wake from Hibernate, and continues operating during reboot. A CSV error detection is reported to the Fault structure.

29.11.49.1.2 CSV_LF_CSV_REF_LIMIT

Description: Clock Supervision Reference Limits
Address: 0x40261724
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	UPPER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	LOWER	RW	RW	0	Cycle time lower limit. Set the lower limit -1, in reference clock cycles, before the next monitored clock event is allowed to happen. If a monitored clock event happens before this limit is reached a CSV error is detected. LOWER must be at least 1 less than UPPER. In case the clocks are asynchronous LOWER must be at least 3 less than UPPER.
16:23	UPPER	RW	RW	0	Cycle time upper limit. Set the upper limit -1, in reference clock cycles, before (or same time) the next monitored clock event must happen. If a monitored clock event does not happen before this limit is reached, or does not happen at all (clock loss), a CSV error is detected.

29.11.49.1.3 CSV_LF_CSV_MON_CTL

Description: Clock Supervision Monitor Control
Address: 0x40261728
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	PERIOD	RW	RW	0	Period time. Set the Period -1, in monitored clock cycles, before the next monitored clock event happens. $PERIOD \leq (UPPER+1) / FREQ\_RATIO - 1$, with $FREQ\_RATIO = (\text{Reference frequency} / \text{Monitored frequency})$ In case the clocks are asynchronous: $PERIOD \leq UPPER / FREQ\_RATIO - 1$ Additionally margin must be added for accuracy of both clocks.

29.11.50 CSV_ILO

29.11.50.1 CSV

29.11.50.1.1 CSV_ILO_CSV_REF_CTL

Description: Clock Supervision Reference Control
Address: 0x40261730
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment: Controls clock supervision for a clock tree.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STARTUP [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CSV_EN [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	STARTUP	RW	RW	0	Startup delay time -1 (in reference clock cycles), after enable, from reference clock start to monitored clock start. At a minimum (both clocks running): $STARTUP \geq (PERIOD + 3) * FREQ\_RATIO - UPPER$, with $FREQ\_RATIO = (Reference\ frequency / Monitored\ frequency)$ On top of that the actual clock startup delay and the margin for accuracy of both clocks must be added.
31	CSV_EN	RW	RW	0	Enables clock supervision, both frequency and loss. CSV in Active domain: Clock supervision is reset during DeepSleep and Hibernate modes. When enabled it begins operating automatically after a DeepSleep wakeup, but it must be reconfigured after Hibernate wakeup. CSV in DeepSleep domain: Clock supervision is reset during Hibernate mode. It must be reconfigured after Hibernate wakeup. CSV in Backup domain: Clock supervision operates during Hibernate mode, can be configured to wake from Hibernate, and continues operating during reboot. A CSV error detection is reported to the Fault structure.

29.11.50.1.2 CSV_ILO_CSV_REF_LIMIT

Description: Clock Supervision Reference Limits
Address: 0x40261734
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	UPPER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	LOWER	RW	RW	0	Cycle time lower limit. Set the lower limit -1, in reference clock cycles, before the next monitored clock event is allowed to happen. If a monitored clock event happens before this limit is reached a CSV error is detected. LOWER must be at least 1 less than UPPER. In case the clocks are asynchronous LOWER must be at least 3 less than UPPER.
16:23	UPPER	RW	RW	0	Cycle time upper limit. Set the upper limit -1, in reference clock cycles, before (or same time) the next monitored clock event must happen. If a monitored clock event does not happen before this limit is reached, or does not happen at all (clock loss), a CSV error is detected.

29.11.50.1.3 CSV_ILO_CSV_MON_CTL

Description: Clock Supervision Monitor Control
Address: 0x40261738
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	PERIOD	RW	RW	0	Period time. Set the Period -1, in monitored clock cycles, before the next monitored clock event happens. $PERIOD \leq (UPPER+1) / FREQ\_RATIO - 1$, with $FREQ\_RATIO = (\text{Reference frequency} / \text{Monitored frequency})$ In case the clocks are asynchronous: $PERIOD \leq UPPER / FREQ\_RATIO - 1$ Additionally margin must be added for accuracy of both clocks.

29.11.51 CLK_PLL400M

29.11.51.1 CLK_PLL400M_CONFIG

Description: 400MHz PLL Configuration Register

Address: 0x40261900

Offset: 0x0

Retention: Retained

IsDeepSleep: No

Comment: This register contains PLL configuration for 400MHz PLL. There is a copy of this register for each 400MHz PLL. Configuration settings should not be changed while it is a selected clock (connected to logic). This prevents clock glitches that can crash the logic.

Default: 0x20116

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FEEDBACK_DIV [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			REFERENCE_DIV [12:8]				
Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			OUTPUT_DIV [20:16]				
Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:30]	BYPASS_SEL [29:28]		None [27:27]	LOCK_DELAY [26:25]		None [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	FEEDBACK_DIV	RW	RW	22	Control bits for feedback divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0-15: illegal (undefined behavior) 16: divide by 16 ... 200: divide by 200 >200: illegal (undefined behavior) When using fractional mode, the jitter specs are met over the restricted range of 27 to 47, inclusive.
8:12	REFERENCE_DIV	RW	RW	1	Control bits for reference divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0: illegal (undefined behavior) 1: divide by 1 ... 16: divide by 16 others: illegal (undefined behavior) When using fractional mode, the jitter specs are met over the restricted range of 1 to 4, inclusive.

Bits	Name	SW	HW	Default or Enum	Description
16:20	OUTPUT_DIV	RW	RW	2	Control bits for Output divider. Set the divide value before enabling the PLL, and do not change it while PLL is enabled. 0: illegal (undefined behavior) 1: illegal (undefined behavior) 2: divide by 2. Suitable for direct usage as HFCLK source. ... 16: divide by 16. Suitable for direct usage as HFCLK source. >16: illegal (undefined behavior)
25:26	LOCK_DELAY	RW	RW	0	Configures the sensitivity of the lock detection logic, according to the intended operating mode: 0: Integer divider without spreading; 1: Fractional division or spreading. 2,3: reserved (do not use)
28:29	BYPASS_SEL	RW	RW	0	Bypass mux located just after PLL output. This selection is glitch-free and can be changed while the PLL is running. When changing BYPASS_SEL, do not turn off the reference clock or PLL clock for five cycles (whichever is slower).
	AUTO			0	Automatic using lock indicator. When unlocked, automatically selects PLL reference input (bypass mode). When locked, automatically selects PLL output. If ENABLE=0, automatically selects PLL reference input.
	LOCKED_OR_NOTHING			1	Similar to AUTO, except the clock is gated off when unlocked. This is compatible with clock supervision, because the supervisors allow no clock during startup (until a timeout occurs), and the clock targets the proper frequency whenever it is running. If ENABLE=0, no clock is output.
	PLL_REF			2	Select PLL reference input (bypass mode). Ignores lock indicator
	PLL_OUT			3	Select PLL output. Ignores lock indicator. If ENABLE=0, no clock is output.
31	ENABLE	RW	RW	0	Master enable for PLL. Setup FEEDBACK_DIV, REFERENCE_DIV, and OUTPUT_DIV at least one cycle before setting ENABLE=1. $f_{OUT} = (FEEDBACK\_DIV + \frac{FRAC\_EN * FRAC\_DIV}{2^{24}}) * (f_{REF} / REFERENCE\_DIV) / (OUTPUT\_DIV)$ 0: Block is disabled. When the PLL disables, hardware controls the bypass mux as described in BYPASS_SEL, before disabling the PLL circuit. 1: Block is enabled

29.11.51.2 CLK_PLL400M_CONFIG2

Description: 400MHz PLL Configuration Register 2
Address: 0x40261904
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: This register contains additional PLL configuration for 400MHz fractional PLLs. There is a copy of this register for each 400MHz PLL. Configure this register before enabling the PLL, and do not change any settings (except FRAC_DIV) while PLL ENABLE==1.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	FRAC_DIV [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	FRAC_DIV [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	FRAC_DIV [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	FRAC_EN [31:31]	FRAC_DITHER_EN [30:28]			None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:23	FRAC_DIV	RW	RW	0	Control bits for fractional divider. This value is interpreted as a fraction of the PFD frequency, i.e. $f_{PFD} * (FRAC\_DIV / 2^{24})$. This field can be dynamically updated within the 1000ppm control limit. It takes up to 115 AHB cycles to transfer the setting to the PLL, and writes that occur faster may be silently ignored and require the application to write again after the previous update has finished. Reading the register returns the accepted value. The PLL will start targeting the new value, but it may take significant time (milliseconds) to stabilize at the new average value. Do not change the FRAC_DIV setting while the PLL is initially locking.
28:30	FRAC_DITHER_EN	RW	RW	0	Enables dithering during fractional operation. 3'b000: disables dithering; 3'b001: enables dithering; others: reserved
31	FRAC_EN	RW	RW	0	Enables fractional division mode. When using fractional division mode, see CLK_PLL400M_CONFIG.LOCK_DELAY for an additional configuration requirement.

29.11.51.3 CLK_PLL400M_CONFIG3

Description: 400MHz PLL Configuration Register 3
Address: 0x40261908
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: This register contains additional PLL configuration for 400MHz fractional PLLs. There is a copy of this register for each 400MHz PLL. There is a copy of this register for each 400MHz PLL. Configure this register before enabling the PLL, and do not change any settings while PLL_ENABLE==1.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	SSCG_DEPTH [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	None [15:10]						SSCG_DEPTH [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:19]					SSCG_RATE [18:16]		
Bits	31	30	29	28	27	26	25	24
Name	SSCG_EN [31:31]	None [30:29]		SSCG_MODE [28:28]	None [27:25]			SSCG_DITHER_EN [24:24]

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:9	SSCG_DEPTH	RW	RW	0	Control bits for SSCG modulation depth as a percentage of the non-modulated clock. The following choices are supported, and all others are reserved: 10'h029: -0.5 percent (down-spread), 10'h052: -1 percent (down-spread), 10'h0a4: -2 percent (down-spread), 10'h0f6: -3 percent (down-spread)
16:18	SSCG_RATE	RW	RW	0	Control bits for SSCG modulation rate as a factor of fPFD clock frequency. Audio applications should choose a setting that results in a modulation rate that is greater than 20kHz, so fPFD/512 or fPFD/256 is recommended. 0: Modulation rate = fPFD/4096, 1: Modulation rate = fPFD/2048, 2: Modulation rate = fPFD/1024, 3: Modulation rate = fPFD/512, 4: Modulation rate = fPFD/256 (limited to 8MHz only), others: reserved
24	SSCG_DITHER_EN	RW	RW	0	Reserved. Setting is not used internally.
28	SSCG_MODE	RW	RW	0	Reserved. Write zero always.
31	SSCG_EN	RW	RW	0	Enables spreading mode. When using spreading, see CLK_PLL400M_CONFIG.LOCK_DELAY for an additional configuration requirement.

29.11.51.4 CLK_PLL400M_STATUS

Description: 400MHz PLL Status Register

Address: 0x4026190C

Offset: 0xC

Retention: Retained

IsDeepSleep: No

Comment: This register indicates status for a PLL400M. There is a copy of this register for each PLL400M. This register is synchronized during an AHB read transaction. This causes a number wait-states to be inserted in the transaction depending on the frequency ration between system and PLL frequency.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						UNLOCK_OC CURRED [1:1]	LOCKED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOCKED	R	R	0	PLL Lock Indicator
1	UNLOCK_OCCURRED	RW1C	RW1C	0	This bit sets whenever the PLL Lock bit goes low, and stays set until cleared by firmware.

29.11.52 MCWDT

29.11.52.1 MCWDT_CPU_SELECT

Description: MCWDT CPU selection register
Address: 0x40268040
Offset: 0x40
Retention: Retained
IsDeepSleep: Yes
Comment: Assigns this MCWDT to a CPU.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						CPU_SEL [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	CPU_SEL	RW	RW	0	Assigns this MCWDT to a CPU. This selects which CPU SLEEPDEEP signal is used for SLEEPDEEP_PAUSE.

29.11.52.2 MCWDT_CTR2_CTL

Description: MCWDT Subcounter 2 Control register
Address: 0x40268080
Offset: 0x80
Retention: Retained
IsDeepSleep: Yes
Comment: Control register for MCWDT subcounter 2. Writes are ignored when locked (i.e. corresponding LOCK.MCWDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_Lf cycles to take effect.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ENABLED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLED	R	R	0	Indicates actual state of this subcounter. May lag ENABLE by up to two clk_Lf cycles.
31	ENABLE	RW	RW	0	Enable subcounter. May take up to 2 clk_Lf cycles to take effect. When ENABLE changes from 1->0, the counter is cleared. 0: Counter is disabled (not clocked) 1: Counter is enabled (counting up)

29.11.52.3 MCWDT_CTR2_CONFIG

Description: MCWDT Subcounter 2 Configuration register
Address: 0x40268084
Offset: 0x84
Retention: Retained
IsDeepSleep: Yes
Comment: Configuration for MCWDT subcounter 2. Writes are ignored when locked (i.e. corresponding LOCK.MCWDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_Lf cycles to take effect. Before changing the limit, it is recommended to set the service bit for this subcounter and wait until it reads back low. This prevents possible unintended actions caused by synchronization delays.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ACTION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:21]			BITS [20:16]				

Bits	31	30	29	28	27	26	25	24
Name	DEBUG_RUN [31:31]	SLEEPDEEP_PAUSE [30:30]	None [29:29]	DEBUG_TRIGGER_EN [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ACTION	RW	RW	0	Action taken when the specified BIT toggles. Action will be triggered on the same edge where BITS to observe toggle.
	NOTHING			0	Do nothing
	INT			1	Trigger an interrupt
16:20	BITS	RW	RW	0	Bit to observe for a toggle: 0: Do ACTION after CNT[0] toggles (i.e. every tick) . 31: Do ACTION after CNT[31] toggles (i.e. every 2 ³¹ ticks)
28	DEBUG_TRIGGER_EN	RW	RW	0	Enables the trigger input for this MCWDT to pause the counter during debug mode. To pause at a breakpoint while debugging, configure the trigger matrix to connect the related CPU halted signal to the trigger input for this MCWDT, and then set this bit. It takes up to two clk_Lf cycles for the trigger signal to be processed. Triggers that are less than two clk_Lf cycles may be missed. Synchronization errors can accumulate each time it is halted. 0: Pauses the counter whenever a debug probe is connected. 1: Pauses the counter whenever a debug probe is connected and the trigger input is high.

Bits	Name	SW	HW	Default or Enum	Description
30	SLEEPDEEP_PAUSE	RW	RW	0	Pauses/runs this counter when the corresponding processor is in SLEEPDEEP. Note it may take up to two clk_If cycles for the counter to pause and up to two clk_If cycles for it to unpause, due to internal synchronization. 0: Counter runs normally regardless of processor mode. 1: Counter pauses when corresponding processor is in SLEEPDEEP.
31	DEBUG_RUN	RW	RW	0	Pauses/runs this counter while a debugger is connected. Other behaviors are unchanged during debugging, including service, configuration updates and enable/disable. Note it may take up to two clk_If cycles for the counter to pause and another two cycles to unpause, due to internal synchronization. 0: When debugger connected, counter pauses incrementing as configured in DEBUG_TRIGGER_EN. 1: When debugger connected, counter increments normally, but reset generation is blocked.

29.11.52.4 MCWDT_CTR2_CNT

Description: MCWDT Subcounter 2 Count Register
Address: 0x40268088
Offset: 0x88
Retention: Retained
IsDeepSleep: Yes
Comment: Count value for this MCWDT subcounter 2. Writes are ignored when this subcounter is enabled or when it is locked (i.e. corresponding LOCK.MCWDT_LOCK<>0).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CNT2 [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CNT2 [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	CNT2 [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CNT2 [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CNT2	RW	RW	0	Current value of subcounter 2 for this MCWDT. This field may lag the actual count value by up to one clk_if cycle, due to internal synchronization. When this subcounter is disabled and unlocked, the count value can be written for verification and debugging purposes. Software writes are always ignored when the subcounter is enabled.

29.11.52.5 MCWDT_LOCK

Description: MCWDT Lock Register
Address: 0x40268090
Offset: 0x90
Retention: Retained
IsDeepSleep: No
Comment: Lock or unlock the respective configuration registers of subcounters 0/1/2 of this MCWDT.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						MCWDT_LOCK [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	MCWDT_LOCK	RW	RW	0	Prohibits writing control and configuration registers related to this MCWDT when not equal 0 (as specified in the other register descriptions). Requires at least two different writes to unlock. Note that this field is 2 bits to force multiple writes only. Each MCWDT has a separate local lock.
	NO_CHG			0	No effect
	CLR0			1	Clears bit 0
	CLR1			2	Clears bit 1
	SET01			3	Sets both bits 0 and 1

29.11.52.6 MCWDT_SERVICE

Description: MCWDT Service Register
Address: 0x40268094
Offset: 0x94
Retention: Retained
IsDeepSleep: Yes
Comment: Control the behavior of the Watchdog counters. Writes to this register are ignored when LOCK.MCWDT_LOCK<>0. All fields in this register can be used while counter is in operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						CTR1_SERVICE [1:1]	CTR0_SERVICE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTR0_SERVICE	RW1S	RW1S	0	Services subcounter 0. This resets the count value for subcounter 0 to zero. This may take up to three clk_if cycles to take effect. Hardware clears this bit, after necessary synchronization. To ensure a pending CTR0_SERVICE write is reflected, firmware should wait until this bit reads low before attempting to write CTR0_SERVICE=1. If subcounter 0 is disabled, CTR0_SERVICE will not trigger a LOWER_ACTION and will not clear a preloaded count value.
1	CTR1_SERVICE	RW1S	RW1S	0	Services subcounter 1. This resets the count value for subcounter 1 to zero. This may take up to three clk_if cycles to take effect. Hardware clears this bit, after necessary synchronization. To ensure a pending CTR1_SERVICE write is reflected, firmware should wait until this bit reads low before attempting to write CTR1_SERVICE=1. If subcounter 1 is disabled, CTR1_SERVICE will not trigger a LOWER_ACTION and will not clear a preloaded count value.

29.11.52.7 MCWDT_INTR

Description: MCWDT Interrupt Register
Address: 0x402680A0
Offset: 0xA0
Retention: Retained
IsDeepSleep: No
Comment: Interrupt status register for MCWDT subcounters.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CTR2_INT [2:2]	CTR1_INT [1:1]	CTR0_INT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTR0_INT	RW1C	RW1C	0	MCWDT Interrupt Request for sub-counter 0. This bit is set by hardware as configured by this registers. This bit must be cleared by firmware.
1	CTR1_INT	RW1C	RW1C	0	MCWDT Interrupt Request for sub-counter 1. This bit is set by hardware as configured by this registers. This bit must be cleared by firmware.
2	CTR2_INT	RW1C	RW1C	0	MCWDT Interrupt Request for sub-counter 2. This bit is set by hardware as configured by this registers. This bit must be cleared by firmware.

29.11.52.8 MCWDT_INTR_SET

Description: MCWDT Interrupt Set Register
Address: 0x402680A4
Offset: 0xA4
Retention: Retained
IsDeepSleep: No
Comment: This register can be used to trigger an interrupt for firmware testing.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CTR2_INT [2:2]	CTR1_INT [1:1]	CTR0_INT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTR0_INT	RW1S	RW1S	0	Set interrupt for MCWDT_INT0
1	CTR1_INT	RW1S	RW1S	0	Set interrupt for MCWDT_INT1
2	CTR2_INT	RW1S	RW1S	0	Set interrupt for MCWDT_INT2

29.11.52.9 MCWDT_INTR_MASK

Description: MCWDT Interrupt Mask Register
Address: 0x402680A8
Offset: 0xA8
Retention: Retained
IsDeepSleep: No
Comment: This register controls whether a subcounter interrupt is forwarded to the corresponding processor. All masks block the interrupt when 0 and forward the interrupt when 1.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CTR2_INT [2:2]	CTR1_INT [1:1]	CTR0_INT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTR0_INT	RW	RW	0	Mask for sub-counter 0 for warning interrupt
1	CTR1_INT	RW	RW	0	Mask for sub-counter 1 for warning interrupt
2	CTR2_INT	RW	RW	0	Mask for sub-counter 2

29.11.52.10 MCWDT_INTR_MASKED

Description: MCWDT Interrupt Masked Register

Address: 0x402680AC

Offset: 0xAC

Retention: Retained

IsDeepSleep: No

Comment: Bitwise AND between the interrupt request and mask registers so firmware can read the status of all mask enabled interrupt causes with a single load operation. Each available MCWDT has a copy of this register.

Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CTR2_INT [2:2]	CTR1_INT [1:1]	CTR0_INT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CTR0_INT	R	R	0	Logical and of corresponding request and mask bits.
1	CTR1_INT	R	R	0	Logical and of corresponding request and mask bits.
2	CTR2_INT	R	R	0	Logical and of corresponding request and mask bits.

29.11.52.11 CTR

29.11.52.11.1 MCWDT_CTR_CTL

Description: MCWDT Subcounter Control Register
Address: 0x40268000
Offset: 0x0
Retention: Retained
IsDeepSleep: Yes
Comment: Control register for this MCWDT subcounter. Writes are ignored when locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_Lf cycles to take effect.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ENABLED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLED	R	R	0	Indicates actual state of this subcounter. May lag ENABLE by up to two clk_Lf cycles.
31	ENABLE	RW	RW	0	Enable subcounter. May take up to 2 clk_Lf cycles to take effect. When ENABLE changes from 1->0, the counter is cleared. 0: Counter is disabled (not clocked) 1: Counter is enabled (counting up)

29.11.52.11.2 MCWDT_CTR_LOWER_LIMIT

Description: MCWDT Subcounter Lower Limit Register
Address: 0x40268004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: Lower limit for this MCWDT subcounter. Writes are ignored when locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_{If} cycles to take effect. Before changing the limit, it is recommended to set the service bit for this subcounter within the configured limits. This prevents possible unintended actions caused by the updated limits.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	LOWER_LIMIT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	LOWER_LIMIT	RW	RW	0	Lower limit for this MCWDT subcounter. See LOWER_ACTION.

29.11.52.11.3 MCWDT_CTR_UPPER_LIMIT

Description: MCWDT Subcounter Upper Limit Register
Address: 0x40268008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: Upper limit for this MCWDT subcounter. Writes are ignored when locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_{If} cycles to take effect. Before changing the limit, it is recommended to set the service bit for this subcounter within the configured limits. This prevents possible unintended actions caused by the updated limits.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UPPER_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	UPPER_LIMIT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	UPPER_LIMIT	RW	RW	0	Upper limit for this MCWDT subcounter. See UPPER_ACTION.

29.11.52.11.4 MCWDT_CTR_WARN_LIMIT

Description: MCWDT Subcounter Warn Limit Register
Address: 0x4026800C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Warn limit for this MCWDT subcounter. Writes are ignored when locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_{If} cycles to take effect. Before changing the limit, it is recommended to set the service bit for this subcounter within the configured limits. This prevents possible unintended actions caused by the updated limits.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WARN_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	WARN_LIMIT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	WARN_LIMIT	RW	RW	0	Warn limit for this MCWDT subcounter. See WARN_ACTION.

29.11.52.11.5 MCWDT_CTR_CONFIG

Description: MCWDT Subcounter Configuration Register
Address: 0x40268010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Configuration for this MCWDT subcounter. Writes are ignored when locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0). This register may be written while the counter is running, but new values may take up to 2 clk_If cycles to take effect. MCWDT always reports the first fault that occurs across subcounter #0 and subcounter #1 for this MCWDT, but may not report additional faults that occur while the first is being processed.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		UPPER_ACTION [5:4]		None [3:2]		LOWER_ACTION [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			AUTO_SERVICE [12:12]	None [11:9]			WARN_ACTION [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DEBUG_RUN [31:31]	SLEEPDEEP_PAUSE [30:30]	None [29:29]	DEBUG_TRIGGER_EN [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	LOWER_ACTION	RW	RW	0	Action taken if this watchdog is serviced before LOWER_LIMIT is reached. LOWER_ACTION is ignored (i.e. treated as NOTHING) when a debugger is connected and/or when the corresponding processor is in SLEEPDEEP.
	NOTHING			0	Do nothing
	FAULT			1	Trigger a fault. It can take up to 3 clk_If cycles for the fault to be transferred to the fault manager. For LOWER_LIMIT >= 1: The action is triggered on same edge when it meets this condition. For LOWER_LIMIT == 0: No action is triggered.
	FAULT_THEN_RESET			2	Trigger a fault. Further, trigger a system-wide reset if the fault is not serviced and the watchdog is not cleared within 6 clk_If cycles. It can take up to 3 clk_If cycles for the fault to be transferred to the fault manager, which gives at least 3 clk_If cycles for software to respond. For LOWER_LIMIT >= 1: The action is triggered on same edge when it meets this condition. For LOWER_LIMIT == 0: No action is triggered.
4:5	UPPER_ACTION	RW	RW	0	Action taken if this watchdog is not serviced before UPPER_LIMIT is reached. The counter stops counting when UPPER_LIMIT is reached, regardless of UPPER_ACTION setting. UPPER_ACTION is ignored (i.e. treated as NOTHING) when a debugger is connected.
	NOTHING			0	Do nothing

Bits	Name	SW	HW	Default or Enum	Description
	FAULT			1	Trigger a fault. For UPPER_LIMIT $\geq$ 2: The action is triggered on same edge when it meets this condition. For UPPER_LIMIT $<$ 2: The action may take up to one extra clk_Lf cycle to trigger.
	FAULT_THEN_RESET			2	Trigger a fault. Further, trigger a system-wide reset if the fault is not serviced and the watchdog is not cleared within 6 clk_Lf cycles. It can take up to 3 clk_Lf cycles for the fault to be transferred to the fault manager, which gives at least 3 clk_Lf cycles for software to respond. For UPPER_LIMIT $\geq$ 2: The action is triggered on same edge when it meets this condition. For UPPER_LIMIT $<$ 2: The action may take up to one extra clk_Lf cycle to trigger.
8	WARN_ACTION	RW	RW	0	Action taken when the count value reaches WARN_LIMIT. The minimum setting to achieve a periodic interrupt is WARN_LIMIT==1. A setting of zero will trigger once but not periodically. For WARN_LIMIT $\geq$ 2: The action is triggered on same edge when it meets this condition. For WARN_LIMIT == [0,1] : The action may take up to one extra clk_Lf cycle to trigger.
	NOTHING			0	Do nothing
	INT			1	Trigger an interrupt.
12	AUTO_SERVICE	RW	RW	0	Automatically service when the count value reaches WARN_LIMIT. This allows creation of a periodic interrupt if this counter is not needed as a watchdog. This field is ignored when LOWER_ACTION $\neq$ NOTHING or when UPPER_ACTION $\neq$ NOTHING.
28	DEBUG_TRIGGER_EN	RW	RW	0	Enables the trigger input for this MCWDT to pause the counter during debug mode. To pause at a breakpoint while debugging, configure the trigger matrix to connect the related CPU halted signal to the trigger input for this MCWDT, and then set this bit. It takes up to two clk_Lf cycles for the trigger signal to be processed. Triggers that are less than two clk_Lf cycles may be missed. Synchronization errors can accumulate each time it is halted. 0: Pauses the counter whenever a debug probe is connected. 1: Pauses the counter whenever a debug probe is connected and the trigger input is high.
30	SLEEPDEEP_PAUSE	RW	RW	0	Pauses/runs this counter when the corresponding processor is in SLEEPDEEP. Note it may take up to two clk_Lf cycles for the counter to pause and up to two clk_Lf cycles for it to unpause, due to internal synchronization. After wakeup, the LOWER_ACTION is ignored until after the first service. This prevents an unintentional trigger of the LOWER_ACTION before the firmware realigns the servicing period. After the first service, LOWER_ACTION behaves as configured. 0: Counter runs normally regardless of processor mode. 1: Counter pauses when corresponding processor is in SLEEPDEEP.

Bits	Name	SW	HW	Default or Enum	Description
31	DEBUG_RUN	RW	RW	0	Pauses/runs this counter while a debugger is connected. Other behaviors are unchanged during debugging, including service, configuration updates and enable/disable. Note it may take up to two clk_If cycles for the counter to pause, due to internal synchronization. When (DEBUG_RUN==1 or DEBUG_TRIGGER_EN==0) and the debugger is connected for at least two clk_If cycles, the LOWER_ACTION is ignored until after the first service after the debugger is disconnected. After the debugger is disconnected, the LOWER_ACTION is ignored until after the first service. This prevents an unintentional trigger of the LOWER_ACTION before the firmware realigns the servicing period. After the first service, LOWER_ACTION behaves as configured. If the debugger is disconnected before two clk_If cycles, the LOWER_ACTION may or may not be ignored. 0: When debugger connected, counter pauses incrementing as configured in DEBUG_TRIGGER_EN. 1: When debugger connected, counter increments normally, but reset generation is blocked. To block LOWER_ACTION fault generation, write DEBUG_TRIGGER_EN==0.

29.11.52.11.6 MCWDT_CTR_CNT

Description: MCWDT Subcounter Count Register
Address: 0x40268014
Offset: 0x14
Retention: Retained
IsDeepSleep: Yes
Comment: Count value for this MCWDT subcounter. Writes are ignored when this subcounter is enabled or when it is locked (i.e. corresponding MCWDT[i]_LOCK.WDT_LOCK<>0).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CNT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CNT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:15	CNT	RW	RW	0	Current value of subcounter for this MCWDT. This field may lag the actual count value by up to one clk cycle, due to internal synchronization. When this subcounter is disabled and unlocked, the count value can be written for verification and debugging purposes. Software writes are always ignored when the subcounter is enabled.

29.11.53 WDT

29.11.53.1 WDT_CTL

Description: WDT Control Register
Address: 0x4026C000
Offset: 0x0
Retention: Retained
IsDeepSleep: Yes
Comment: Control register for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0).
Default: 0x80000001

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							ENABLED [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	ENABLE [31:31]	None [30:24]						

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	ENABLED	R	R	1	Indicates actual state of watchdog. May lag ENABLE by up to three clk_ilo0 cycles.
31	ENABLE	RW	RW	1	Enable watchdog. May take up to three clk_ilo0 cycles to take effect. When ENABLE changes from 1->0, the counter is cleared. Do not enter DEEPSLEEP or HIBERNATE mode if ENABLE<>ENABLED. This can be done by waiting until ENABLE==ENABLED whenever ENABLE is changed. 0: Counter is disabled (not clocked). 1: Counter is enabled (counting up)

29.11.53.2 WDT_LOWER_LIMIT

Description: WDT Lower Limit Register
Address: 0x4026C004
Offset: 0x4
Retention: Retained
IsDeepSleep: No
Comment: Lower limit for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0) or when enabled (i.e. ENABLE==1 and ENABLED==1).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	LOWER_LIMIT [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	LOWER_LIMIT [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	LOWER_LIMIT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	LOWER_LIMIT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	LOWER_LIMIT	RW	RW	0	Lower limit for watchdog. See LOWER_ACTION.

29.11.53.3 WDT_UPPER_LIMIT

Description: WDT Upper Limit Register
Address: 0x4026C008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment: Upper limit for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0) or when enabled (i.e. ENABLE==1 and ENABLED==1).
Default: 0x8000

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	UPPER_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	UPPER_LIMIT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	UPPER_LIMIT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	UPPER_LIMIT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	UPPER_LIMIT	RW	RW	32768	Upper limit for watchdog. See UPPER_ACTION.

29.11.53.4 WDT_WARN_LIMIT

Description: WDT Warn Limit Register
Address: 0x4026C00C
Offset: 0xC
Retention: Retained
IsDeepSleep: No
Comment: Warn limit for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0) or when enabled (i.e. ENABLE==1 and ENABLED==1).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	WARN_LIMIT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	WARN_LIMIT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	WARN_LIMIT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	WARN_LIMIT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	WARN_LIMIT	RW	RW	0	Warn limit for watchdog. See WARN_ACTION.

29.11.53.5 WDT_CONFIG

Description: WDT Configuration Register
Address: 0x4026C010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment: Configuration for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0) or when enabled (i.e. ENABLE==1 and ENABLED==1).
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:5]			UPPER_ACTION [4:4]	None [3:1]			LOWER_ACTION [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:13]			AUTO_SERVICE [12:12]	None [11:9]			WARN_ACTION [8:8]

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DEBUG_RUN [31:31]	HIB_PAUSE [30:30]	DPSLP_PAUSE [29:29]	DEBUG_TRIGGER_EN [28:28]	None [27:24]			

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	LOWER_ACTION	RW	RW	0	Action taken if this watchdog is serviced before LOWER_LIMIT is reached. LOWER_ACTION is ignored (i.e. treated as NOTHING) when a debugger is connected and/or when the chip is in DEEPSLEEP/HIBERNATE modes. For LOWER_LIMIT >= 1: The action is triggered on same edge when it meets this condition. For LOWER_LIMIT == 0: No action is triggered.
	NOTHING			0	Do nothing
	RESET			1	Trigger a reset.
4	UPPER_ACTION	RW	RW	1	Action taken if this watchdog is not serviced before UPPER_LIMIT is reached. The counter stops counting when UPPER_LIMIT is reached, regardless of UPPER_ACTION setting. UPPER_ACTION is ignored (i.e. treated as NOTHING) when a debugger is connected. For UPPER_LIMIT >= 2: The action is triggered on same edge when it meets this condition. For UPPER_LIMIT < 2: The action may take up to one extra clk_ilo0 cycle to trigger.
	NOTHING			0	Do nothing
	RESET			1	Trigger a reset.

Bits	Name	SW	HW	Default or Enum	Description
8	WARN_ACTION	RW	RW	0	Action taken when the count value reaches WARN_LIMIT. The minimum setting to achieve a periodic interrupt is WARN_LIMIT==1. A setting of zero will trigger once but not periodically. For WARN_LIMIT >= 2: The action is triggered on same edge when it meets this condition. For WARN_LIMIT < 2 : The action may take up to one extra clk_ilo0 cycle to trigger.
	NOTHING			0	Do nothing
	INT			1	Trigger an interrupt.
12	AUTO_SERVICE	RW	RW	0	Automatically service when the count value reaches WARN_LIMIT. This allows creation of a periodic interrupt if this counter is not needed as a watchdog. This field is ignored when LOWER_ACTION<>NOTHING or when UPPER_ACTION<>NOTHING.
28	DEBUG_TRIGGER_EN	RW	RW	0	Enables the trigger input for WDT to pause the counter during debug mode. To pause at a breakpoint while debugging, configure the trigger matrix to connect the related CPU halted signal to the trigger input for this WDT, and then set this bit. It takes up to two clk_ilo0 cycles for the trigger signal to be processed. Triggers that are less than two clk_ilo0 cycles may be missed. Synchronization error can accumulate each time it is halted. 0: Pauses the counter whenever a debug probe is connected. 1: Pauses the counter whenever a debug probe is connected and the trigger input is high.
29	DPSLP_PAUSE	RW	RW	0	Pauses/runs this counter when the system is in DEEPSLEEP. Note it may take up to two clk_ilo0 cycles for the counter to pause, due to internal synchronization. During DEEPSLEEP wakeup, the pause request is removed when clk_hf0 starts clocking, and then it may take up to two clk_ilo0 cycles for the counter to start. After wakeup, the LOWER_ACTION is ignored until after the first service. This prevents an unintentional trigger of the LOWER_ACTION before the firmware realigns the servicing period. After the first service, LOWER_ACTION behaves as configured. 0: Counter behaves normally during DEEPSLEEP. 1: Counter pauses during DEEPSLEEP.
30	HIB_PAUSE	RW	RW	0	Pauses/runs this counter when the system is in HIBERNATE. Note it may take up to two clk_ilo0 cycles for the counter to pause, due to internal synchronization. After wakeup, the LOWER_ACTION is ignored until after the first service. This prevents an unintentional trigger of the LOWER_ACTION before the firmware realigns the servicing period. After the first service, LOWER_ACTION behaves as configured. 0: Counter behaves normally during HIBERNATE. 1: Counter pauses during HIBERNATE.

Bits	Name	SW	HW	Default or Enum	Description
31	DEBUG_RUN	RW	RW	0	Pauses/runs this counter while a debugger is connected. Other behaviors are unchanged during debugging, including service, configuration updates and enable/disable. Note it may take up to two clk_ilo0 cycles for the counter to pause and another two cycles to unpause, due to internal synchronization. If the debugger is connected for at least two clk_ilo0 cycles, the LOWER_ACTION is ignored until after the first service after the debugger is disconnected. This prevents an unintentional trigger of the LOWER_ACTION before the firmware realigns the servicing period. After the first service, LOWER_ACTION behaves as configured. If the debugger is disconnected before two clk_ilo0 cycles, the LOWER_ACTION may or may not be ignored. 0: When debugger connected, counter pauses incrementing as configured in DEBUG_TRIGGER_EN. 1: When debugger connected, counter increments normally, but reset generation is blocked.

29.11.53.6 WDT_CNT

Description: WDT Count Register
Address: 0x4026C014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment: Count value for watchdog. Writes are ignored when locked (i.e. Corresponding LOCK.WDT_LOCK<>0) or when enabled (i.e. ENABLE==1 and ENABLED==1).
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CNT [7:0]							
Bits	15	14	13	12	11	10	9	8
Name	CNT [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	CNT [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	CNT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CNT	RW	RW	0	Current value of subcounter for this WDT. This field may lag the actual count value by up to one clk_ilo0 cycle, due to internal synchronization. When this subcounter is disabled and unlocked, the count value can be written for verification and debugging purposes. Software writes are always ignored when the subcounter is enabled.

29.11.53.7 WDT_LOCK

Description: WDT Lock register
Address: 0x4026C040
Offset: 0x40
Retention: Retained
IsDeepSleep: No
Comment: Lock or unlock the registers in this WDT
Default: 0x3

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:2]						WDT_LOCK [1:0]	

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	WDT_LOCK	RW	RW	3	Prohibits writing control and configuration registers related to this WDT when not equal 0 (as specified in the other register descriptions). Requires at least two different writes to unlock. Note that this field is 2 bits to force multiple writes only. This register also locks the clk_ilo0 settings.
	NO_CHG			0	No effect
	CLR0			1	Clears bit 0
	CLR1			2	Clears bit 1
	SET01			3	Sets both bits 0 and 1

29.11.53.8 WDT_SERVICE

Description: WDT Service register
Address: 0x4026C044
Offset: 0x44
Retention: Retained
IsDeepSleep: Yes
Comment: Control the behavior of the Watchdog counters. Writes to this register are ignored when LOCK.WDT_LOCK<>0. All fields in this register can be used while counter is in operation.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							SERVICE [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	SERVICE	RW1S	RW1S	0	Services the watchdog. This resets the count value to zero. This may take up to three clk_ilo0 cycle to take effect. Hardware clears this bit, after necessary synchronization. To ensure a pending SERVICE write is reflected, firmware should wait until this bit reads low before attempting to write SERVICE=1. If WDT is disabled, SERVICE will not trigger a LOWER_ACTION and will not clear a preloaded count value.

29.11.53.9 WDT_INTR

Description: WDT Interrupt Register
Address: 0x4026C050
Offset: 0x50
Retention: Retained
IsDeepSleep: No
Comment: Interrupt signal from WDT
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WDT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WDT	RW1C	RW1C	0	WDT Interrupt Request. This bit is set as configured by WDT action and limits. Due to internal synchronization, it takes up to 8 SYSCLK cycles to update after a W1C or reading this register and during this time AHB bus is stalled.

29.11.53.10 WDT_INTR_SET

Description: WDT Interrupt Set Register
Address: 0x4026C054
Offset: 0x54
Retention: Retained
IsDeepSleep: No
Comment: Can be used to set interrupts for firmware testing.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WDT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WDT	RW1S	RW1S	0	Set interrupt. Due to internal synchronization, it takes up to 8 SYSCLK cycles to update after a W1S or reading from this register and during this time AHB bus is stalled.

29.11.53.11 WDT_INTR_MASK

Description: WDT Interrupt Mask Register
Address: 0x4026C058
Offset: 0x58
Retention: Retained
IsDeepSleep: No
Comment: Controls whether interrupt is forwarded to CPU. All masks block the interrupt when 0 and forward the interrupt when 1
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WDT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WDT	RW	RW	0	Mask for watchdog timer. Clearing this bit will not forward the interrupt to the CPU.

29.11.53.12 WDT_INTR_MASKED

Description: WDT Interrupt Masked Register
Address: 0x4026C05C
Offset: 0x5C
Retention: Retained
IsDeepSleep: No
Comment: Bitwise AND between the interrupt request and mask registers so firmware can read the status of all mask enabled interrupt causes with a single load operation
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:1]							WDT [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	WDT	R	R	0	Logical and of corresponding request and mask bits. Due to internal synchronization, it takes up to 8 SYSCLK cycles to read from this register. During this time AHB bus is stalled.

30 SYSAP

Description	System debug Access Port (SYSAP) registers
Base Address	0xE0000000
Size	0x20000000
Slave Num	SYSTEM

30.1 ROMTABLE

Register Name	Address	Permission	Description
SYSAP_ROMTABLE_DID	0xF1000FCC	FULL	Device Type Identifier register.
SYSAP_ROMTABLE_PID4	0xF1000FD0	FULL	Peripheral Identification Register 4.
SYSAP_ROMTABLE_PID5	0xF1000FD4	FULL	Peripheral Identification Register 5.
SYSAP_ROMTABLE_PID6	0xF1000FD8	FULL	Peripheral Identification Register 6.
SYSAP_ROMTABLE_PID7	0xF1000FDC	FULL	Peripheral Identification Register 7.
SYSAP_ROMTABLE_PID0	0xF1000FE0	FULL	Peripheral Identification Register 0.
SYSAP_ROMTABLE_PID1	0xF1000FE4	FULL	Peripheral Identification Register 1.
SYSAP_ROMTABLE_PID2	0xF1000FE8	FULL	Peripheral Identification Register 2.
SYSAP_ROMTABLE_PID3	0xF1000FEC	FULL	Peripheral Identification Register 3.
SYSAP_ROMTABLE_CID0	0xF1000FF0	FULL	Component Identification Register 0.
SYSAP_ROMTABLE_CID1	0xF1000FF4	FULL	Component Identification Register 1.
SYSAP_ROMTABLE_CID2	0xF1000FF8	FULL	Component Identification Register 2.
SYSAP_ROMTABLE_CID3	0xF1000FFC	FULL	Component Identification Register 3.

30.2 Register Details

30.2.1 ROMTABLE

30.2.1.1 SYSAP_ROMTABLE_DID

Description: Device Type Identifier register.
Address: 0xF1000FCC
Offset: 0xFCC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	1	.

30.2.1.2 SYSAP_ROMTABLE_PID4

Description: Peripheral Identification Register 4.
Address: 0xF1000FD0
Offset: 0xFD0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNT [7:4]				JEP_CONTINUATION [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	JEP_CONTINUATION	R	R	Undefined	JEP106 continuation code. This value is product specific and specified as part of the product definition in the CPUSS.JEPCONTINUATION parameter.
4:7	COUNT	R	R	0	Size of ROM Table is $2^{\text{COUNT}} * 4$ KByte.

30.2.1.3 SYSAP_ROMTABLE_PID5

Description: Peripheral Identification Register 5.
Address: 0xF1000FD4
Offset: 0xFD4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

30.2.1.4 SYSAP_ROMTABLE_PID6

Description: Peripheral Identification Register 6.
Address: 0xF1000FD8
Offset: 0xFD8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

30.2.1.5 SYSAP_ROMTABLE_PID7

Description: Peripheral Identification Register 7.
Address: 0xF1000FDC
Offset: 0xFDC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	0	.

30.2.1.6 SYSAP_ROMTABLE_PID0

Description: Peripheral Identification Register 0.
Address: 0xF1000FE0
Offset: 0xFE0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PN_MIN [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	PN_MIN	R	R	Undefined	JEP106 part number. 4 lsb of CPUSS.PARTNUMBER parameter. These part numbers are maintained in spec 40-9500.

30.2.1.7 SYSAP_ROMTABLE_PID1

Description: Peripheral Identification Register 1.
Address: 0xF1000FE4
Offset: 0xFE4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	JEPID_MIN [7:4]				PN_MAJ [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	PN_MAJ	R	R	Undefined	JEP106 part number. 4 msbs of CPUSS.PARTNUMBER parameter. These part numbers are maintained in spec 40-9500.
4:7	JEPID_MIN	R	R	Undefined	JEP106 vendor id. 4 lsbs of CPUSS.JEPID parameter. This number is maintained in spec 40-9500.

30.2.1.8 SYSAP_ROMTABLE_PID2

Description: Peripheral Identification Register 2.
Address: 0xF100FE8
Offset: 0xFE8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REV [7:4]				None [3:3]	JEPID_MAJ [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	JEPID_MAJ	R	R	Undefined	JEP106 vendor id. 4 msbs of CPUSS.JEPID parameter. This number is maintained in spec 40-9500.
4:7	REV	R	R	Undefined	Major REVersion number (chip specific). Identifies the design iteration of the component. For first tape out: 0x1. This field is implemented in RTL by an ECO-able tie-off structure and is incremented on subsequent tape outs.

30.2.1.9 SYSAP_ROMTABLE_PID3

Description: Peripheral Identification Register 3.
Address: 0xF100FEC
Offset: 0xFEC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	REV_AND [7:4]				CM [3:0]			

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:3	CM	R	R	0	N/A
4:7	REV_AND	R	R	Undefined	Minor REVersion number (chip specific). For first tape out: 0x1. This field is incremented on subsequent tape outs.

30.2.1.10 SYSAP_ROMTABLE_CID0

Description: Component Identification Register 0.
Address: 0xF1000FF0
Offset: 0xFF0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xD

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	13	Component identification byte 0 of 4-byte component identification 0xB105:100D.

30.2.1.11 SYSAP_ROMTABLE_CID1

Description: Component Identification Register 1.
Address: 0xF1000FF4
Offset: 0xFF4
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x10

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	16	Component identification byte 1 of 4-byte component identification 0xB105:100D. Component class: 'ROM Table'.

30.2.1.12 SYSAP_ROMTABLE_CID2

Description: Component Identification Register 2.
Address: 0xF1000FF8
Offset: 0xFF8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x5

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	5	Component identification byte 2 of 4-byte component identification 0xB105:100D.

30.2.1.13 SYSAP_ROMTABLE_CID3

Description: Component Identification Register 3.
Address: 0xF1000FFC
Offset: 0xFFC
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xB1

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	VALUE [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	VALUE [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	VALUE [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	VALUE [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	VALUE	R	R	177	Component identification byte 3 of 4-byte component identification 0xB105:100D.

31 TCPWM

Description	Timer/Counter/PWM
Base Address	0x40580000
Size	0x20000
Slave Num	MMIO5 - 3

31.1 GRP 0

31.1.1 CNT 0

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT0_CTRL	0x40580000	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT0_STATUS	0x40580004	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT0_COUNTER	0x40580008	FULL	Counter count register
TCPWM0_GRP0_CNT0_CC0	0x40580010	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT0_CC0_BUFF	0x40580014	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT0_CC1	0x40580018	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT0_CC1_BUFF	0x4058001C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT0_PERIOD	0x40580020	FULL	Counter period register
TCPWM0_GRP0_CNT0_PERIOD_BUFF	0x40580024	FULL	Counter buffered period register
TCPWM0_GRP0_CNT0_DT	0x40580030	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT0_TR_CMD	0x40580040	FULL	Counter trigger command register
TCPWM0_GRP0_CNT0_TR_IN_SEL0	0x40580044	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT0_TR_IN_SEL1	0x40580048	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT0_TR_IN_EDGE_SEL	0x4058004C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT0_TR_PWM_CTRL	0x40580050	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT0_TR_OUT_SEL	0x40580054	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT0_INTR	0x40580070	FULL	Interrupt request register
TCPWM0_GRP0_CNT0_INTR_SET	0x40580074	FULL	Interrupt set request register
TCPWM0_GRP0_CNT0_INTR_MASK	0x40580078	FULL	Interrupt mask register
TCPWM0_GRP0_CNT0_INTR_MASKED	0x4058007C	FULL	Interrupt masked request register

31.1.2 CNT 1

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT1_CTRL	0x40580080	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT1_STATUS	0x40580084	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT1_COUNTER	0x40580088	FULL	Counter count register
TCPWM0_GRP0_CNT1_CC0	0x40580090	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT1_CC0_BUFF	0x40580094	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT1_CC1	0x40580098	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT1_CC1_BUFF	0x4058009C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT1_PERIOD	0x405800A0	FULL	Counter period register
TCPWM0_GRP0_CNT1_PERIOD_BUFF	0x405800A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT1_DT	0x405800B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT1_TR_CMD	0x405800C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT1_TR_IN_SEL0	0x405800C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT1_TR_IN_SEL1	0x405800C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT1_TR_IN_EDGE_SEL	0x405800CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT1_TR_PWM_CTRL	0x405800D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT1_TR_OUT_SEL	0x405800D4	FULL	Counter output trigger selection register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT1_INTR	0x405800F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT1_INTR_SET	0x405800F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT1_INTR_MASK	0x405800F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT1_INTR_MASKED	0x405800FC	FULL	Interrupt masked request register

31.1.3 CNT 2

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT2_CTRL	0x40580100	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT2_STATUS	0x40580104	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT2_COUNTER	0x40580108	FULL	Counter count register
TCPWM0_GRP0_CNT2_CC0	0x40580110	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT2_CC0_BUFF	0x40580114	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT2_CC1	0x40580118	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT2_CC1_BUFF	0x4058011C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT2_PERIOD	0x40580120	FULL	Counter period register
TCPWM0_GRP0_CNT2_PERIOD_BUFF	0x40580124	FULL	Counter buffered period register
TCPWM0_GRP0_CNT2_DT	0x40580130	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT2_TR_CMD	0x40580140	FULL	Counter trigger command register
TCPWM0_GRP0_CNT2_TR_IN_SEL0	0x40580144	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT2_TR_IN_SEL1	0x40580148	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT2_TR_IN_EDGE_SEL	0x4058014C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT2_TR_PWM_CTRL	0x40580150	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT2_TR_OUT_SEL	0x40580154	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT2_INTR	0x40580170	FULL	Interrupt request register
TCPWM0_GRP0_CNT2_INTR_SET	0x40580174	FULL	Interrupt set request register
TCPWM0_GRP0_CNT2_INTR_MASK	0x40580178	FULL	Interrupt mask register
TCPWM0_GRP0_CNT2_INTR_MASKED	0x4058017C	FULL	Interrupt masked request register

31.1.4 CNT 3

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT3_CTRL	0x40580180	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT3_STATUS	0x40580184	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT3_COUNTER	0x40580188	FULL	Counter count register
TCPWM0_GRP0_CNT3_CC0	0x40580190	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT3_CC0_BUFF	0x40580194	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT3_CC1	0x40580198	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT3_CC1_BUFF	0x4058019C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT3_PERIOD	0x405801A0	FULL	Counter period register
TCPWM0_GRP0_CNT3_PERIOD_BUFF	0x405801A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT3_DT	0x405801B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT3_TR_CMD	0x405801C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT3_TR_IN_SEL0	0x405801C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT3_TR_IN_SEL1	0x405801C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT3_TR_IN_EDGE_SEL	0x405801CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT3_TR_PWM_CTRL	0x405801D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT3_TR_OUT_SEL	0x405801D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT3_INTR	0x405801F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT3_INTR_SET	0x405801F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT3_INTR_MASK	0x405801F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT3_INTR_MASKED	0x405801FC	FULL	Interrupt masked request register

31.1.5 CNT 4

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT4_CTRL	0x40580200	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT4_STATUS	0x40580204	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT4_COUNTER	0x40580208	FULL	Counter count register
TCPWM0_GRP0_CNT4_CC0	0x40580210	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT4_CC0_BUFF	0x40580214	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT4_CC1	0x40580218	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT4_CC1_BUFF	0x4058021C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT4_PERIOD	0x40580220	FULL	Counter period register
TCPWM0_GRP0_CNT4_PERIOD_BUFF	0x40580224	FULL	Counter buffered period register
TCPWM0_GRP0_CNT4_DT	0x40580230	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT4_TR_CMD	0x40580240	FULL	Counter trigger command register
TCPWM0_GRP0_CNT4_TR_IN_SEL0	0x40580244	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT4_TR_IN_SEL1	0x40580248	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT4_TR_IN_EDGE_SEL	0x4058024C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT4_TR_PWM_CTRL	0x40580250	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT4_TR_OUT_SEL	0x40580254	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT4_INTR	0x40580270	FULL	Interrupt request register
TCPWM0_GRP0_CNT4_INTR_SET	0x40580274	FULL	Interrupt set request register
TCPWM0_GRP0_CNT4_INTR_MASK	0x40580278	FULL	Interrupt mask register
TCPWM0_GRP0_CNT4_INTR_MASKED	0x4058027C	FULL	Interrupt masked request register

31.1.6 CNT 5

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT5_CTRL	0x40580280	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT5_STATUS	0x40580284	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT5_COUNTER	0x40580288	FULL	Counter count register
TCPWM0_GRP0_CNT5_CC0	0x40580290	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT5_CC0_BUFF	0x40580294	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT5_CC1	0x40580298	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT5_CC1_BUFF	0x4058029C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT5_PERIOD	0x405802A0	FULL	Counter period register
TCPWM0_GRP0_CNT5_PERIOD_BUFF	0x405802A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT5_DT	0x405802B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT5_TR_CMD	0x405802C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT5_TR_IN_SEL0	0x405802C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT5_TR_IN_SEL1	0x405802C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT5_TR_IN_EDGE_SEL	0x405802CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT5_TR_PWM_CTRL	0x405802D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT5_TR_OUT_SEL	0x405802D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT5_INTR	0x405802F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT5_INTR_SET	0x405802F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT5_INTR_MASK	0x405802F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT5_INTR_MASKED	0x405802FC	FULL	Interrupt masked request register

31.1.7 CNT 6

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT6_CTRL	0x40580300	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT6_STATUS	0x40580304	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT6_COUNTER	0x40580308	FULL	Counter count register
TCPWM0_GRP0_CNT6_CC0	0x40580310	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT6_CC0_BUFF	0x40580314	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT6_CC1	0x40580318	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT6_CC1_BUFF	0x4058031C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT6_PERIOD	0x40580320	FULL	Counter period register
TCPWM0_GRP0_CNT6_PERIOD_BUFF	0x40580324	FULL	Counter buffered period register
TCPWM0_GRP0_CNT6_DT	0x40580330	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT6_TR_CMD	0x40580340	FULL	Counter trigger command register
TCPWM0_GRP0_CNT6_TR_IN_SEL0	0x40580344	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT6_TR_IN_SEL1	0x40580348	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT6_TR_IN_EDGE_SEL	0x4058034C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT6_TR_PWM_CTRL	0x40580350	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT6_TR_OUT_SEL	0x40580354	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT6_INTR	0x40580370	FULL	Interrupt request register
TCPWM0_GRP0_CNT6_INTR_SET	0x40580374	FULL	Interrupt set request register
TCPWM0_GRP0_CNT6_INTR_MASK	0x40580378	FULL	Interrupt mask register
TCPWM0_GRP0_CNT6_INTR_MASKED	0x4058037C	FULL	Interrupt masked request register

31.1.8 CNT 7

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT7_CTRL	0x40580380	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT7_STATUS	0x40580384	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT7_COUNTER	0x40580388	FULL	Counter count register
TCPWM0_GRP0_CNT7_CC0	0x40580390	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT7_CC0_BUFF	0x40580394	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT7_CC1	0x40580398	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT7_CC1_BUFF	0x4058039C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT7_PERIOD	0x405803A0	FULL	Counter period register
TCPWM0_GRP0_CNT7_PERIOD_BUFF	0x405803A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT7_DT	0x405803B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT7_TR_CMD	0x405803C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT7_TR_IN_SEL0	0x405803C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT7_TR_IN_SEL1	0x405803C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT7_TR_IN_EDGE_SEL	0x405803CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT7_TR_PWM_CTRL	0x405803D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT7_TR_OUT_SEL	0x405803D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT7_INTR	0x405803F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT7_INTR_SET	0x405803F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT7_INTR_MASK	0x405803F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT7_INTR_MASKED	0x405803FC	FULL	Interrupt masked request register

31.1.9 CNT 8

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT8_CTRL	0x40580400	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT8_STATUS	0x40580404	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT8_COUNTER	0x40580408	FULL	Counter count register
TCPWM0_GRP0_CNT8_CC0	0x40580410	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT8_CC0_BUFF	0x40580414	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT8_CC1	0x40580418	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT8_CC1_BUFF	0x4058041C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT8_PERIOD	0x40580420	FULL	Counter period register
TCPWM0_GRP0_CNT8_PERIOD_BUFF	0x40580424	FULL	Counter buffered period register
TCPWM0_GRP0_CNT8_DT	0x40580430	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT8_TR_CMD	0x40580440	FULL	Counter trigger command register
TCPWM0_GRP0_CNT8_TR_IN_SEL0	0x40580444	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT8_TR_IN_SEL1	0x40580448	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT8_TR_IN_EDGE_SEL	0x4058044C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT8_TR_PWM_CTRL	0x40580450	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT8_TR_OUT_SEL	0x40580454	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT8_INTR	0x40580470	FULL	Interrupt request register
TCPWM0_GRP0_CNT8_INTR_SET	0x40580474	FULL	Interrupt set request register
TCPWM0_GRP0_CNT8_INTR_MASK	0x40580478	FULL	Interrupt mask register
TCPWM0_GRP0_CNT8_INTR_MASKED	0x4058047C	FULL	Interrupt masked request register

31.1.10 CNT 9

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT9_CTRL	0x40580480	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT9_STATUS	0x40580484	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT9_COUNTER	0x40580488	FULL	Counter count register
TCPWM0_GRP0_CNT9_CC0	0x40580490	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT9_CC0_BUFF	0x40580494	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT9_CC1	0x40580498	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT9_CC1_BUFF	0x4058049C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT9_PERIOD	0x405804A0	FULL	Counter period register
TCPWM0_GRP0_CNT9_PERIOD_BUFF	0x405804A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT9_DT	0x405804B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT9_TR_CMD	0x405804C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT9_TR_IN_SEL0	0x405804C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT9_TR_IN_SEL1	0x405804C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT9_TR_IN_EDGE_SEL	0x405804CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT9_TR_PWM_CTRL	0x405804D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT9_TR_OUT_SEL	0x405804D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT9_INTR	0x405804F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT9_INTR_SET	0x405804F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT9_INTR_MASK	0x405804F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT9_INTR_MASKED	0x405804FC	FULL	Interrupt masked request register

31.1.11 CNT 10

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT10_CTRL	0x40580500	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT10_STATUS	0x40580504	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT10_COUNTER	0x40580508	FULL	Counter count register
TCPWM0_GRP0_CNT10_CC0	0x40580510	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT10_CC0_BUFF	0x40580514	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT10_CC1	0x40580518	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT10_CC1_BUFF	0x4058051C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT10_PERIOD	0x40580520	FULL	Counter period register
TCPWM0_GRP0_CNT10_PERIOD_BUFF	0x40580524	FULL	Counter buffered period register
TCPWM0_GRP0_CNT10_DT	0x40580530	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT10_TR_CMD	0x40580540	FULL	Counter trigger command register
TCPWM0_GRP0_CNT10_TR_IN_SEL0	0x40580544	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT10_TR_IN_SEL1	0x40580548	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT10_TR_IN_EDGE_SEL	0x4058054C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT10_TR_PWM_CTRL	0x40580550	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT10_TR_OUT_SEL	0x40580554	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT10_INTR	0x40580570	FULL	Interrupt request register
TCPWM0_GRP0_CNT10_INTR_SET	0x40580574	FULL	Interrupt set request register
TCPWM0_GRP0_CNT10_INTR_MASK	0x40580578	FULL	Interrupt mask register
TCPWM0_GRP0_CNT10_INTR_MASKED	0x4058057C	FULL	Interrupt masked request register

31.1.12 CNT 11

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT11_CTRL	0x40580580	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT11_STATUS	0x40580584	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT11_COUNTER	0x40580588	FULL	Counter count register
TCPWM0_GRP0_CNT11_CC0	0x40580590	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT11_CC0_BUFF	0x40580594	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT11_CC1	0x40580598	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT11_CC1_BUFF	0x4058059C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT11_PERIOD	0x405805A0	FULL	Counter period register
TCPWM0_GRP0_CNT11_PERIOD_BUFF	0x405805A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT11_DT	0x405805B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT11_TR_CMD	0x405805C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT11_TR_IN_SEL0	0x405805C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT11_TR_IN_SEL1	0x405805C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT11_TR_IN_EDGE_SEL	0x405805CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT11_TR_PWM_CTRL	0x405805D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT11_TR_OUT_SEL	0x405805D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT11_INTR	0x405805F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT11_INTR_SET	0x405805F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT11_INTR_MASK	0x405805F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT11_INTR_MASKED	0x405805FC	FULL	Interrupt masked request register

31.1.13 CNT 12

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT12_CTRL	0x40580600	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT12_STATUS	0x40580604	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT12_COUNTER	0x40580608	FULL	Counter count register
TCPWM0_GRP0_CNT12_CC0	0x40580610	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT12_CC0_BUFF	0x40580614	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT12_CC1	0x40580618	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT12_CC1_BUFF	0x4058061C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT12_PERIOD	0x40580620	FULL	Counter period register
TCPWM0_GRP0_CNT12_PERIOD_BUFF	0x40580624	FULL	Counter buffered period register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT12_DT	0x40580630	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT12_TR_CMD	0x40580640	FULL	Counter trigger command register
TCPWM0_GRP0_CNT12_TR_IN_SEL0	0x40580644	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT12_TR_IN_SEL1	0x40580648	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT12_TR_IN_EDGE_SEL	0x4058064C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT12_TR_PWM_CTRL	0x40580650	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT12_TR_OUT_SEL	0x40580654	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT12_INTR	0x40580670	FULL	Interrupt request register
TCPWM0_GRP0_CNT12_INTR_SET	0x40580674	FULL	Interrupt set request register
TCPWM0_GRP0_CNT12_INTR_MASK	0x40580678	FULL	Interrupt mask register
TCPWM0_GRP0_CNT12_INTR_MASKED	0x4058067C	FULL	Interrupt masked request register

31.1.14 CNT 13

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT13_CTRL	0x40580680	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT13_STATUS	0x40580684	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT13_COUNTER	0x40580688	FULL	Counter count register
TCPWM0_GRP0_CNT13_CC0	0x40580690	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT13_CC0_BUFF	0x40580694	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT13_CC1	0x40580698	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT13_CC1_BUFF	0x4058069C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT13_PERIOD	0x405806A0	FULL	Counter period register
TCPWM0_GRP0_CNT13_PERIOD_BUFF	0x405806A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT13_DT	0x405806B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT13_TR_CMD	0x405806C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT13_TR_IN_SEL0	0x405806C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT13_TR_IN_SEL1	0x405806C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT13_TR_IN_EDGE_SEL	0x405806CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT13_TR_PWM_CTRL	0x405806D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT13_TR_OUT_SEL	0x405806D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT13_INTR	0x405806F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT13_INTR_SET	0x405806F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT13_INTR_MASK	0x405806F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT13_INTR_MASKED	0x405806FC	FULL	Interrupt masked request register

31.1.15 CNT 14

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT14_CTRL	0x40580700	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT14_STATUS	0x40580704	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT14_COUNTER	0x40580708	FULL	Counter count register
TCPWM0_GRP0_CNT14_CC0	0x40580710	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT14_CC0_BUFF	0x40580714	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT14_CC1	0x40580718	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT14_CC1_BUFF	0x4058071C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT14_PERIOD	0x40580720	FULL	Counter period register
TCPWM0_GRP0_CNT14_PERIOD_BUFF	0x40580724	FULL	Counter buffered period register
TCPWM0_GRP0_CNT14_DT	0x40580730	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT14_TR_CMD	0x40580740	FULL	Counter trigger command register
TCPWM0_GRP0_CNT14_TR_IN_SEL0	0x40580744	FULL	Counter input trigger selection register 0

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT14_TR_IN_SEL1	0x40580748	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT14_TR_IN_EDGE_SEL	0x4058074C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT14_TR_PWM_CTRL	0x40580750	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT14_TR_OUT_SEL	0x40580754	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT14_INTR	0x40580770	FULL	Interrupt request register
TCPWM0_GRP0_CNT14_INTR_SET	0x40580774	FULL	Interrupt set request register
TCPWM0_GRP0_CNT14_INTR_MASK	0x40580778	FULL	Interrupt mask register
TCPWM0_GRP0_CNT14_INTR_MASKED	0x4058077C	FULL	Interrupt masked request register

31.1.16 CNT 15

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT15_CTRL	0x40580780	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT15_STATUS	0x40580784	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT15_COUNTER	0x40580788	FULL	Counter count register
TCPWM0_GRP0_CNT15_CC0	0x40580790	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT15_CC0_BUFF	0x40580794	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT15_CC1	0x40580798	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT15_CC1_BUFF	0x4058079C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT15_PERIOD	0x405807A0	FULL	Counter period register
TCPWM0_GRP0_CNT15_PERIOD_BUFF	0x405807A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT15_DT	0x405807B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT15_TR_CMD	0x405807C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT15_TR_IN_SEL0	0x405807C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT15_TR_IN_SEL1	0x405807C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT15_TR_IN_EDGE_SEL	0x405807CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT15_TR_PWM_CTRL	0x405807D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT15_TR_OUT_SEL	0x405807D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT15_INTR	0x405807F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT15_INTR_SET	0x405807F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT15_INTR_MASK	0x405807F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT15_INTR_MASKED	0x405807FC	FULL	Interrupt masked request register

31.1.17 CNT 16

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT16_CTRL	0x40580800	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT16_STATUS	0x40580804	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT16_COUNTER	0x40580808	FULL	Counter count register
TCPWM0_GRP0_CNT16_CC0	0x40580810	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT16_CC0_BUFF	0x40580814	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT16_CC1	0x40580818	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT16_CC1_BUFF	0x4058081C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT16_PERIOD	0x40580820	FULL	Counter period register
TCPWM0_GRP0_CNT16_PERIOD_BUFF	0x40580824	FULL	Counter buffered period register
TCPWM0_GRP0_CNT16_DT	0x40580830	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT16_TR_CMD	0x40580840	FULL	Counter trigger command register
TCPWM0_GRP0_CNT16_TR_IN_SEL0	0x40580844	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT16_TR_IN_SEL1	0x40580848	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT16_TR_IN_EDGE_SEL	0x4058084C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT16_TR_PWM_CTRL	0x40580850	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT16_TR_OUT_SEL	0x40580854	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT16_INTR	0x40580870	FULL	Interrupt request register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT16_INTR_SET	0x40580874	FULL	Interrupt set request register
TCPWM0_GRP0_CNT16_INTR_MASK	0x40580878	FULL	Interrupt mask register
TCPWM0_GRP0_CNT16_INTR_MASKED	0x4058087C	FULL	Interrupt masked request register

31.1.18 CNT 17

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT17_CTRL	0x40580880	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT17_STATUS	0x40580884	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT17_COUNTER	0x40580888	FULL	Counter count register
TCPWM0_GRP0_CNT17_CC0	0x40580890	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT17_CC0_BUFF	0x40580894	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT17_CC1	0x40580898	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT17_CC1_BUFF	0x4058089C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT17_PERIOD	0x405808A0	FULL	Counter period register
TCPWM0_GRP0_CNT17_PERIOD_BUFF	0x405808A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT17_DT	0x405808B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT17_TR_CMD	0x405808C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT17_TR_IN_SEL0	0x405808C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT17_TR_IN_SEL1	0x405808C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT17_TR_IN_EDGE_SEL	0x405808CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT17_TR_PWM_CTRL	0x405808D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT17_TR_OUT_SEL	0x405808D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT17_INTR	0x405808F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT17_INTR_SET	0x405808F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT17_INTR_MASK	0x405808F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT17_INTR_MASKED	0x405808FC	FULL	Interrupt masked request register

31.1.19 CNT 18

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT18_CTRL	0x40580900	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT18_STATUS	0x40580904	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT18_COUNTER	0x40580908	FULL	Counter count register
TCPWM0_GRP0_CNT18_CC0	0x40580910	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT18_CC0_BUFF	0x40580914	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT18_CC1	0x40580918	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT18_CC1_BUFF	0x4058091C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT18_PERIOD	0x40580920	FULL	Counter period register
TCPWM0_GRP0_CNT18_PERIOD_BUFF	0x40580924	FULL	Counter buffered period register
TCPWM0_GRP0_CNT18_DT	0x40580930	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT18_TR_CMD	0x40580940	FULL	Counter trigger command register
TCPWM0_GRP0_CNT18_TR_IN_SEL0	0x40580944	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT18_TR_IN_SEL1	0x40580948	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT18_TR_IN_EDGE_SEL	0x4058094C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT18_TR_PWM_CTRL	0x40580950	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT18_TR_OUT_SEL	0x40580954	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT18_INTR	0x40580970	FULL	Interrupt request register
TCPWM0_GRP0_CNT18_INTR_SET	0x40580974	FULL	Interrupt set request register
TCPWM0_GRP0_CNT18_INTR_MASK	0x40580978	FULL	Interrupt mask register
TCPWM0_GRP0_CNT18_INTR_MASKED	0x4058097C	FULL	Interrupt masked request register

31.1.20 CNT 19

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT19_CTRL	0x40580980	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT19_STATUS	0x40580984	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT19_COUNTER	0x40580988	FULL	Counter count register
TCPWM0_GRP0_CNT19_CC0	0x40580990	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT19_CC0_BUFF	0x40580994	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT19_CC1	0x40580998	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT19_CC1_BUFF	0x4058099C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT19_PERIOD	0x405809A0	FULL	Counter period register
TCPWM0_GRP0_CNT19_PERIOD_BUFF	0x405809A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT19_DT	0x405809B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT19_TR_CMD	0x405809C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT19_TR_IN_SEL0	0x405809C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT19_TR_IN_SEL1	0x405809C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT19_TR_IN_EDGE_SEL	0x405809CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT19_TR_PWM_CTRL	0x405809D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT19_TR_OUT_SEL	0x405809D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT19_INTR	0x405809F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT19_INTR_SET	0x405809F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT19_INTR_MASK	0x405809F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT19_INTR_MASKED	0x405809FC	FULL	Interrupt masked request register

31.1.21 CNT 20

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT20_CTRL	0x40580A00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT20_STATUS	0x40580A04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT20_COUNTER	0x40580A08	FULL	Counter count register
TCPWM0_GRP0_CNT20_CC0	0x40580A10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT20_CC0_BUFF	0x40580A14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT20_CC1	0x40580A18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT20_CC1_BUFF	0x40580A1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT20_PERIOD	0x40580A20	FULL	Counter period register
TCPWM0_GRP0_CNT20_PERIOD_BUFF	0x40580A24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT20_DT	0x40580A30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT20_TR_CMD	0x40580A40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT20_TR_IN_SEL0	0x40580A44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT20_TR_IN_SEL1	0x40580A48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT20_TR_IN_EDGE_SEL	0x40580A4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT20_TR_PWM_CTRL	0x40580A50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT20_TR_OUT_SEL	0x40580A54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT20_INTR	0x40580A70	FULL	Interrupt request register
TCPWM0_GRP0_CNT20_INTR_SET	0x40580A74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT20_INTR_MASK	0x40580A78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT20_INTR_MASKED	0x40580A7C	FULL	Interrupt masked request register

31.1.22 CNT 21

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT21_CTRL	0x40580A80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT21_STATUS	0x40580A84	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT21_COUNTER	0x40580A88	FULL	Counter count register
TCPWM0_GRP0_CNT21_CC0	0x40580A90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT21_CC0_BUFF	0x40580A94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT21_CC1	0x40580A98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT21_CC1_BUFF	0x40580A9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT21_PERIOD	0x40580AA0	FULL	Counter period register
TCPWM0_GRP0_CNT21_PERIOD_BUFF	0x40580AA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT21_DT	0x40580AB0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT21_TR_CMD	0x40580AC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT21_TR_IN_SEL0	0x40580AC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT21_TR_IN_SEL1	0x40580AC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT21_TR_IN_EDGE_SEL	0x40580ACC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT21_TR_PWM_CTRL	0x40580AD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT21_TR_OUT_SEL	0x40580AD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT21_INTR	0x40580AF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT21_INTR_SET	0x40580AF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT21_INTR_MASK	0x40580AF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT21_INTR_MASKED	0x40580AFC	FULL	Interrupt masked request register

31.1.23 CNT 22

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT22_CTRL	0x40580B00	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT22_STATUS	0x40580B04	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT22_COUNTER	0x40580B08	FULL	Counter count register
TCPWM0_GRP0_CNT22_CC0	0x40580B10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT22_CC0_BUFF	0x40580B14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT22_CC1	0x40580B18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT22_CC1_BUFF	0x40580B1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT22_PERIOD	0x40580B20	FULL	Counter period register
TCPWM0_GRP0_CNT22_PERIOD_BUFF	0x40580B24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT22_DT	0x40580B30	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT22_TR_CMD	0x40580B40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT22_TR_IN_SEL0	0x40580B44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT22_TR_IN_SEL1	0x40580B48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT22_TR_IN_EDGE_SEL	0x40580B4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT22_TR_PWM_CTRL	0x40580B50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT22_TR_OUT_SEL	0x40580B54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT22_INTR	0x40580B70	FULL	Interrupt request register
TCPWM0_GRP0_CNT22_INTR_SET	0x40580B74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT22_INTR_MASK	0x40580B78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT22_INTR_MASKED	0x40580B7C	FULL	Interrupt masked request register

31.1.24 CNT 23

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT23_CTRL	0x40580B80	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT23_STATUS	0x40580B84	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT23_COUNTER	0x40580B88	FULL	Counter count register
TCPWM0_GRP0_CNT23_CC0	0x40580B90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT23_CC0_BUFF	0x40580B94	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT23_CC1	0x40580B98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT23_CC1_BUFF	0x40580B9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT23_PERIOD	0x40580BA0	FULL	Counter period register
TCPWM0_GRP0_CNT23_PERIOD_BUFF	0x40580BA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT23_DT	0x40580BB0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT23_TR_CMD	0x40580BC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT23_TR_IN_SEL0	0x40580BC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT23_TR_IN_SEL1	0x40580BC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT23_TR_IN_EDGE_SEL	0x40580BCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT23_TR_PWM_CTRL	0x40580BD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT23_TR_OUT_SEL	0x40580BD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT23_INTR	0x40580BF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT23_INTR_SET	0x40580BF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT23_INTR_MASK	0x40580BF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT23_INTR_MASKED	0x40580BFC	FULL	Interrupt masked request register

31.1.25 CNT 24

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT24_CTRL	0x40580C00	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT24_STATUS	0x40580C04	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT24_COUNTER	0x40580C08	FULL	Counter count register
TCPWM0_GRP0_CNT24_CC0	0x40580C10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT24_CC0_BUFF	0x40580C14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT24_CC1	0x40580C18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT24_CC1_BUFF	0x40580C1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT24_PERIOD	0x40580C20	FULL	Counter period register
TCPWM0_GRP0_CNT24_PERIOD_BUFF	0x40580C24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT24_DT	0x40580C30	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT24_TR_CMD	0x40580C40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT24_TR_IN_SEL0	0x40580C44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT24_TR_IN_SEL1	0x40580C48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT24_TR_IN_EDGE_SEL	0x40580C4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT24_TR_PWM_CTRL	0x40580C50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT24_TR_OUT_SEL	0x40580C54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT24_INTR	0x40580C70	FULL	Interrupt request register
TCPWM0_GRP0_CNT24_INTR_SET	0x40580C74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT24_INTR_MASK	0x40580C78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT24_INTR_MASKED	0x40580C7C	FULL	Interrupt masked request register

31.1.26 CNT 25

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT25_CTRL	0x40580C80	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT25_STATUS	0x40580C84	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT25_COUNTER	0x40580C88	FULL	Counter count register
TCPWM0_GRP0_CNT25_CC0	0x40580C90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT25_CC0_BUFF	0x40580C94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT25_CC1	0x40580C98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT25_CC1_BUFF	0x40580C9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT25_PERIOD	0x40580CA0	FULL	Counter period register
TCPWM0_GRP0_CNT25_PERIOD_BUFF	0x40580CA4	FULL	Counter buffered period register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT25_DT	0x40580CB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT25_TR_CMD	0x40580CC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT25_TR_IN_SEL0	0x40580CC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT25_TR_IN_SEL1	0x40580CC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT25_TR_IN_EDGE_SEL	0x40580CCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT25_TR_PWM_CTRL	0x40580CD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT25_TR_OUT_SEL	0x40580CD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT25_INTR	0x40580CF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT25_INTR_SET	0x40580CF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT25_INTR_MASK	0x40580CF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT25_INTR_MASKED	0x40580CFC	FULL	Interrupt masked request register

31.1.27 CNT 26

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT26_CTRL	0x40580D00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT26_STATUS	0x40580D04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT26_COUNTER	0x40580D08	FULL	Counter count register
TCPWM0_GRP0_CNT26_CC0	0x40580D10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT26_CC0_BUFF	0x40580D14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT26_CC1	0x40580D18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT26_CC1_BUFF	0x40580D1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT26_PERIOD	0x40580D20	FULL	Counter period register
TCPWM0_GRP0_CNT26_PERIOD_BUFF	0x40580D24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT26_DT	0x40580D30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT26_TR_CMD	0x40580D40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT26_TR_IN_SEL0	0x40580D44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT26_TR_IN_SEL1	0x40580D48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT26_TR_IN_EDGE_SEL	0x40580D4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT26_TR_PWM_CTRL	0x40580D50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT26_TR_OUT_SEL	0x40580D54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT26_INTR	0x40580D70	FULL	Interrupt request register
TCPWM0_GRP0_CNT26_INTR_SET	0x40580D74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT26_INTR_MASK	0x40580D78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT26_INTR_MASKED	0x40580D7C	FULL	Interrupt masked request register

31.1.28 CNT 27

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT27_CTRL	0x40580D80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT27_STATUS	0x40580D84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT27_COUNTER	0x40580D88	FULL	Counter count register
TCPWM0_GRP0_CNT27_CC0	0x40580D90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT27_CC0_BUFF	0x40580D94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT27_CC1	0x40580D98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT27_CC1_BUFF	0x40580D9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT27_PERIOD	0x40580DA0	FULL	Counter period register
TCPWM0_GRP0_CNT27_PERIOD_BUFF	0x40580DA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT27_DT	0x40580DB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT27_TR_CMD	0x40580DC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT27_TR_IN_SEL0	0x40580DC4	FULL	Counter input trigger selection register 0

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT27_TR_IN_SEL1	0x40580DC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT27_TR_IN_EDGE_SEL	0x40580DCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT27_TR_PWM_CTRL	0x40580DD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT27_TR_OUT_SEL	0x40580DD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT27_INTR	0x40580DF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT27_INTR_SET	0x40580DF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT27_INTR_MASK	0x40580DF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT27_INTR_MASKED	0x40580DFC	FULL	Interrupt masked request register

31.1.29 CNT 28

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT28_CTRL	0x40580E00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT28_STATUS	0x40580E04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT28_COUNTER	0x40580E08	FULL	Counter count register
TCPWM0_GRP0_CNT28_CC0	0x40580E10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT28_CC0_BUFF	0x40580E14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT28_CC1	0x40580E18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT28_CC1_BUFF	0x40580E1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT28_PERIOD	0x40580E20	FULL	Counter period register
TCPWM0_GRP0_CNT28_PERIOD_BUFF	0x40580E24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT28_DT	0x40580E30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT28_TR_CMD	0x40580E40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT28_TR_IN_SEL0	0x40580E44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT28_TR_IN_SEL1	0x40580E48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT28_TR_IN_EDGE_SEL	0x40580E4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT28_TR_PWM_CTRL	0x40580E50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT28_TR_OUT_SEL	0x40580E54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT28_INTR	0x40580E70	FULL	Interrupt request register
TCPWM0_GRP0_CNT28_INTR_SET	0x40580E74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT28_INTR_MASK	0x40580E78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT28_INTR_MASKED	0x40580E7C	FULL	Interrupt masked request register

31.1.30 CNT 29

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT29_CTRL	0x40580E80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT29_STATUS	0x40580E84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT29_COUNTER	0x40580E88	FULL	Counter count register
TCPWM0_GRP0_CNT29_CC0	0x40580E90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT29_CC0_BUFF	0x40580E94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT29_CC1	0x40580E98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT29_CC1_BUFF	0x40580E9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT29_PERIOD	0x40580EA0	FULL	Counter period register
TCPWM0_GRP0_CNT29_PERIOD_BUFF	0x40580EA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT29_DT	0x40580EB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT29_TR_CMD	0x40580EC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT29_TR_IN_SEL0	0x40580EC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT29_TR_IN_SEL1	0x40580EC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT29_TR_IN_EDGE_SEL	0x40580ECC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT29_TR_PWM_CTRL	0x40580ED0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT29_TR_OUT_SEL	0x40580ED4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT29_INTR	0x40580EF0	FULL	Interrupt request register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT29_INTR_SET	0x40580EF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT29_INTR_MASK	0x40580EF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT29_INTR_MASKED	0x40580EFC	FULL	Interrupt masked request register

31.1.31 CNT 30

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT30_CTRL	0x40580F00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT30_STATUS	0x40580F04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT30_COUNTER	0x40580F08	FULL	Counter count register
TCPWM0_GRP0_CNT30_CC0	0x40580F10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT30_CC0_BUFF	0x40580F14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT30_CC1	0x40580F18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT30_CC1_BUFF	0x40580F1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT30_PERIOD	0x40580F20	FULL	Counter period register
TCPWM0_GRP0_CNT30_PERIOD_BUFF	0x40580F24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT30_DT	0x40580F30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT30_TR_CMD	0x40580F40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT30_TR_IN_SEL0	0x40580F44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT30_TR_IN_SEL1	0x40580F48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT30_TR_IN_EDGE_SEL	0x40580F4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT30_TR_PWM_CTRL	0x40580F50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT30_TR_OUT_SEL	0x40580F54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT30_INTR	0x40580F70	FULL	Interrupt request register
TCPWM0_GRP0_CNT30_INTR_SET	0x40580F74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT30_INTR_MASK	0x40580F78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT30_INTR_MASKED	0x40580F7C	FULL	Interrupt masked request register

31.1.32 CNT 31

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT31_CTRL	0x40580F80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT31_STATUS	0x40580F84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT31_COUNTER	0x40580F88	FULL	Counter count register
TCPWM0_GRP0_CNT31_CC0	0x40580F90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT31_CC0_BUFF	0x40580F94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT31_CC1	0x40580F98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT31_CC1_BUFF	0x40580F9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT31_PERIOD	0x40580FA0	FULL	Counter period register
TCPWM0_GRP0_CNT31_PERIOD_BUFF	0x40580FA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT31_DT	0x40580FB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT31_TR_CMD	0x40580FC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT31_TR_IN_SEL0	0x40580FC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT31_TR_IN_SEL1	0x40580FC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT31_TR_IN_EDGE_SEL	0x40580FCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT31_TR_PWM_CTRL	0x40580FD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT31_TR_OUT_SEL	0x40580FD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT31_INTR	0x40580FF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT31_INTR_SET	0x40580FF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT31_INTR_MASK	0x40580FF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT31_INTR_MASKED	0x40580FFC	FULL	Interrupt masked request register

31.1.33 CNT 32

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT32_CTRL	0x40581000	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT32_STATUS	0x40581004	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT32_COUNTER	0x40581008	FULL	Counter count register
TCPWM0_GRP0_CNT32_CC0	0x40581010	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT32_CC0_BUFF	0x40581014	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT32_CC1	0x40581018	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT32_CC1_BUFF	0x4058101C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT32_PERIOD	0x40581020	FULL	Counter period register
TCPWM0_GRP0_CNT32_PERIOD_BUFF	0x40581024	FULL	Counter buffered period register
TCPWM0_GRP0_CNT32_DT	0x40581030	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT32_TR_CMD	0x40581040	FULL	Counter trigger command register
TCPWM0_GRP0_CNT32_TR_IN_SEL0	0x40581044	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT32_TR_IN_SEL1	0x40581048	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT32_TR_IN_EDGE_SEL	0x4058104C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT32_TR_PWM_CTRL	0x40581050	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT32_TR_OUT_SEL	0x40581054	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT32_INTR	0x40581070	FULL	Interrupt request register
TCPWM0_GRP0_CNT32_INTR_SET	0x40581074	FULL	Interrupt set request register
TCPWM0_GRP0_CNT32_INTR_MASK	0x40581078	FULL	Interrupt mask register
TCPWM0_GRP0_CNT32_INTR_MASKED	0x4058107C	FULL	Interrupt masked request register

31.1.34 CNT 33

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT33_CTRL	0x40581080	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT33_STATUS	0x40581084	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT33_COUNTER	0x40581088	FULL	Counter count register
TCPWM0_GRP0_CNT33_CC0	0x40581090	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT33_CC0_BUFF	0x40581094	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT33_CC1	0x40581098	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT33_CC1_BUFF	0x4058109C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT33_PERIOD	0x405810A0	FULL	Counter period register
TCPWM0_GRP0_CNT33_PERIOD_BUFF	0x405810A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT33_DT	0x405810B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT33_TR_CMD	0x405810C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT33_TR_IN_SEL0	0x405810C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT33_TR_IN_SEL1	0x405810C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT33_TR_IN_EDGE_SEL	0x405810CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT33_TR_PWM_CTRL	0x405810D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT33_TR_OUT_SEL	0x405810D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT33_INTR	0x405810F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT33_INTR_SET	0x405810F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT33_INTR_MASK	0x405810F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT33_INTR_MASKED	0x405810FC	FULL	Interrupt masked request register

31.1.35 CNT 34

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT34_CTRL	0x40581100	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT34_STATUS	0x40581104	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT34_COUNTER	0x40581108	FULL	Counter count register
TCPWM0_GRP0_CNT34_CC0	0x40581110	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT34_CC0_BUFF	0x40581114	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT34_CC1	0x40581118	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT34_CC1_BUFF	0x4058111C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT34_PERIOD	0x40581120	FULL	Counter period register
TCPWM0_GRP0_CNT34_PERIOD_BUFF	0x40581124	FULL	Counter buffered period register
TCPWM0_GRP0_CNT34_DT	0x40581130	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT34_TR_CMD	0x40581140	FULL	Counter trigger command register
TCPWM0_GRP0_CNT34_TR_IN_SEL0	0x40581144	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT34_TR_IN_SEL1	0x40581148	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT34_TR_IN_EDGE_SEL	0x4058114C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT34_TR_PWM_CTRL	0x40581150	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT34_TR_OUT_SEL	0x40581154	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT34_INTR	0x40581170	FULL	Interrupt request register
TCPWM0_GRP0_CNT34_INTR_SET	0x40581174	FULL	Interrupt set request register
TCPWM0_GRP0_CNT34_INTR_MASK	0x40581178	FULL	Interrupt mask register
TCPWM0_GRP0_CNT34_INTR_MASKED	0x4058117C	FULL	Interrupt masked request register

31.1.36 CNT 35

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT35_CTRL	0x40581180	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT35_STATUS	0x40581184	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT35_COUNTER	0x40581188	FULL	Counter count register
TCPWM0_GRP0_CNT35_CC0	0x40581190	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT35_CC0_BUFF	0x40581194	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT35_CC1	0x40581198	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT35_CC1_BUFF	0x4058119C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT35_PERIOD	0x405811A0	FULL	Counter period register
TCPWM0_GRP0_CNT35_PERIOD_BUFF	0x405811A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT35_DT	0x405811B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT35_TR_CMD	0x405811C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT35_TR_IN_SEL0	0x405811C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT35_TR_IN_SEL1	0x405811C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT35_TR_IN_EDGE_SEL	0x405811CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT35_TR_PWM_CTRL	0x405811D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT35_TR_OUT_SEL	0x405811D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT35_INTR	0x405811F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT35_INTR_SET	0x405811F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT35_INTR_MASK	0x405811F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT35_INTR_MASKED	0x405811FC	FULL	Interrupt masked request register

31.1.37 CNT 36

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT36_CTRL	0x40581200	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT36_STATUS	0x40581204	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT36_COUNTER	0x40581208	FULL	Counter count register
TCPWM0_GRP0_CNT36_CC0	0x40581210	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT36_CC0_BUFF	0x40581214	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT36_CC1	0x40581218	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT36_CC1_BUFF	0x4058121C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT36_PERIOD	0x40581220	FULL	Counter period register
TCPWM0_GRP0_CNT36_PERIOD_BUFF	0x40581224	FULL	Counter buffered period register
TCPWM0_GRP0_CNT36_DT	0x40581230	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT36_TR_CMD	0x40581240	FULL	Counter trigger command register
TCPWM0_GRP0_CNT36_TR_IN_SEL0	0x40581244	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT36_TR_IN_SEL1	0x40581248	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT36_TR_IN_EDGE_SEL	0x4058124C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT36_TR_PWM_CTRL	0x40581250	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT36_TR_OUT_SEL	0x40581254	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT36_INTR	0x40581270	FULL	Interrupt request register
TCPWM0_GRP0_CNT36_INTR_SET	0x40581274	FULL	Interrupt set request register
TCPWM0_GRP0_CNT36_INTR_MASK	0x40581278	FULL	Interrupt mask register
TCPWM0_GRP0_CNT36_INTR_MASKED	0x4058127C	FULL	Interrupt masked request register

31.1.38 CNT 37

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT37_CTRL	0x40581280	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT37_STATUS	0x40581284	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT37_COUNTER	0x40581288	FULL	Counter count register
TCPWM0_GRP0_CNT37_CC0	0x40581290	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT37_CC0_BUFF	0x40581294	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT37_CC1	0x40581298	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT37_CC1_BUFF	0x4058129C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT37_PERIOD	0x405812A0	FULL	Counter period register
TCPWM0_GRP0_CNT37_PERIOD_BUFF	0x405812A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT37_DT	0x405812B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT37_TR_CMD	0x405812C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT37_TR_IN_SEL0	0x405812C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT37_TR_IN_SEL1	0x405812C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT37_TR_IN_EDGE_SEL	0x405812CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT37_TR_PWM_CTRL	0x405812D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT37_TR_OUT_SEL	0x405812D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT37_INTR	0x405812F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT37_INTR_SET	0x405812F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT37_INTR_MASK	0x405812F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT37_INTR_MASKED	0x405812FC	FULL	Interrupt masked request register

31.1.39 CNT 38

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT38_CTRL	0x40581300	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT38_STATUS	0x40581304	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT38_COUNTER	0x40581308	FULL	Counter count register
TCPWM0_GRP0_CNT38_CC0	0x40581310	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT38_CC0_BUFF	0x40581314	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT38_CC1	0x40581318	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT38_CC1_BUFF	0x4058131C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT38_PERIOD	0x40581320	FULL	Counter period register
TCPWM0_GRP0_CNT38_PERIOD_BUFF	0x40581324	FULL	Counter buffered period register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT38_DT	0x40581330	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT38_TR_CMD	0x40581340	FULL	Counter trigger command register
TCPWM0_GRP0_CNT38_TR_IN_SEL0	0x40581344	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT38_TR_IN_SEL1	0x40581348	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT38_TR_IN_EDGE_SEL	0x4058134C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT38_TR_PWM_CTRL	0x40581350	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT38_TR_OUT_SEL	0x40581354	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT38_INTR	0x40581370	FULL	Interrupt request register
TCPWM0_GRP0_CNT38_INTR_SET	0x40581374	FULL	Interrupt set request register
TCPWM0_GRP0_CNT38_INTR_MASK	0x40581378	FULL	Interrupt mask register
TCPWM0_GRP0_CNT38_INTR_MASKED	0x4058137C	FULL	Interrupt masked request register

31.1.40 CNT 39

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT39_CTRL	0x40581380	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT39_STATUS	0x40581384	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT39_COUNTER	0x40581388	FULL	Counter count register
TCPWM0_GRP0_CNT39_CC0	0x40581390	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT39_CC0_BUFF	0x40581394	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT39_CC1	0x40581398	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT39_CC1_BUFF	0x4058139C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT39_PERIOD	0x405813A0	FULL	Counter period register
TCPWM0_GRP0_CNT39_PERIOD_BUFF	0x405813A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT39_DT	0x405813B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT39_TR_CMD	0x405813C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT39_TR_IN_SEL0	0x405813C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT39_TR_IN_SEL1	0x405813C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT39_TR_IN_EDGE_SEL	0x405813CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT39_TR_PWM_CTRL	0x405813D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT39_TR_OUT_SEL	0x405813D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT39_INTR	0x405813F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT39_INTR_SET	0x405813F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT39_INTR_MASK	0x405813F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT39_INTR_MASKED	0x405813FC	FULL	Interrupt masked request register

31.1.41 CNT 40

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT40_CTRL	0x40581400	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT40_STATUS	0x40581404	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT40_COUNTER	0x40581408	FULL	Counter count register
TCPWM0_GRP0_CNT40_CC0	0x40581410	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT40_CC0_BUFF	0x40581414	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT40_CC1	0x40581418	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT40_CC1_BUFF	0x4058141C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT40_PERIOD	0x40581420	FULL	Counter period register
TCPWM0_GRP0_CNT40_PERIOD_BUFF	0x40581424	FULL	Counter buffered period register
TCPWM0_GRP0_CNT40_DT	0x40581430	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT40_TR_CMD	0x40581440	FULL	Counter trigger command register
TCPWM0_GRP0_CNT40_TR_IN_SEL0	0x40581444	FULL	Counter input trigger selection register 0

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT40_TR_IN_SEL1	0x40581448	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT40_TR_IN_EDGE_SEL	0x4058144C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT40_TR_PWM_CTRL	0x40581450	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT40_TR_OUT_SEL	0x40581454	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT40_INTR	0x40581470	FULL	Interrupt request register
TCPWM0_GRP0_CNT40_INTR_SET	0x40581474	FULL	Interrupt set request register
TCPWM0_GRP0_CNT40_INTR_MASK	0x40581478	FULL	Interrupt mask register
TCPWM0_GRP0_CNT40_INTR_MASKED	0x4058147C	FULL	Interrupt masked request register

31.1.42 CNT 41

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT41_CTRL	0x40581480	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT41_STATUS	0x40581484	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT41_COUNTER	0x40581488	FULL	Counter count register
TCPWM0_GRP0_CNT41_CC0	0x40581490	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT41_CC0_BUFF	0x40581494	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT41_CC1	0x40581498	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT41_CC1_BUFF	0x4058149C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT41_PERIOD	0x405814A0	FULL	Counter period register
TCPWM0_GRP0_CNT41_PERIOD_BUFF	0x405814A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT41_DT	0x405814B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT41_TR_CMD	0x405814C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT41_TR_IN_SEL0	0x405814C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT41_TR_IN_SEL1	0x405814C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT41_TR_IN_EDGE_SEL	0x405814CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT41_TR_PWM_CTRL	0x405814D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT41_TR_OUT_SEL	0x405814D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT41_INTR	0x405814F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT41_INTR_SET	0x405814F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT41_INTR_MASK	0x405814F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT41_INTR_MASKED	0x405814FC	FULL	Interrupt masked request register

31.1.43 CNT 42

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT42_CTRL	0x40581500	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT42_STATUS	0x40581504	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT42_COUNTER	0x40581508	FULL	Counter count register
TCPWM0_GRP0_CNT42_CC0	0x40581510	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT42_CC0_BUFF	0x40581514	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT42_CC1	0x40581518	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT42_CC1_BUFF	0x4058151C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT42_PERIOD	0x40581520	FULL	Counter period register
TCPWM0_GRP0_CNT42_PERIOD_BUFF	0x40581524	FULL	Counter buffered period register
TCPWM0_GRP0_CNT42_DT	0x40581530	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT42_TR_CMD	0x40581540	FULL	Counter trigger command register
TCPWM0_GRP0_CNT42_TR_IN_SEL0	0x40581544	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT42_TR_IN_SEL1	0x40581548	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT42_TR_IN_EDGE_SEL	0x4058154C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT42_TR_PWM_CTRL	0x40581550	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT42_TR_OUT_SEL	0x40581554	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT42_INTR	0x40581570	FULL	Interrupt request register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT42_INTR_SET	0x40581574	FULL	Interrupt set request register
TCPWM0_GRP0_CNT42_INTR_MASK	0x40581578	FULL	Interrupt mask register
TCPWM0_GRP0_CNT42_INTR_MASKED	0x4058157C	FULL	Interrupt masked request register

31.1.44 CNT 43

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT43_CTRL	0x40581580	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT43_STATUS	0x40581584	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT43_COUNTER	0x40581588	FULL	Counter count register
TCPWM0_GRP0_CNT43_CC0	0x40581590	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT43_CC0_BUFF	0x40581594	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT43_CC1	0x40581598	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT43_CC1_BUFF	0x4058159C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT43_PERIOD	0x405815A0	FULL	Counter period register
TCPWM0_GRP0_CNT43_PERIOD_BUFF	0x405815A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT43_DT	0x405815B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT43_TR_CMD	0x405815C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT43_TR_IN_SEL0	0x405815C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT43_TR_IN_SEL1	0x405815C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT43_TR_IN_EDGE_SEL	0x405815CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT43_TR_PWM_CTRL	0x405815D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT43_TR_OUT_SEL	0x405815D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT43_INTR	0x405815F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT43_INTR_SET	0x405815F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT43_INTR_MASK	0x405815F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT43_INTR_MASKED	0x405815FC	FULL	Interrupt masked request register

31.1.45 CNT 44

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT44_CTRL	0x40581600	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT44_STATUS	0x40581604	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT44_COUNTER	0x40581608	FULL	Counter count register
TCPWM0_GRP0_CNT44_CC0	0x40581610	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT44_CC0_BUFF	0x40581614	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT44_CC1	0x40581618	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT44_CC1_BUFF	0x4058161C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT44_PERIOD	0x40581620	FULL	Counter period register
TCPWM0_GRP0_CNT44_PERIOD_BUFF	0x40581624	FULL	Counter buffered period register
TCPWM0_GRP0_CNT44_DT	0x40581630	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT44_TR_CMD	0x40581640	FULL	Counter trigger command register
TCPWM0_GRP0_CNT44_TR_IN_SEL0	0x40581644	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT44_TR_IN_SEL1	0x40581648	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT44_TR_IN_EDGE_SEL	0x4058164C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT44_TR_PWM_CTRL	0x40581650	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT44_TR_OUT_SEL	0x40581654	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT44_INTR	0x40581670	FULL	Interrupt request register
TCPWM0_GRP0_CNT44_INTR_SET	0x40581674	FULL	Interrupt set request register
TCPWM0_GRP0_CNT44_INTR_MASK	0x40581678	FULL	Interrupt mask register
TCPWM0_GRP0_CNT44_INTR_MASKED	0x4058167C	FULL	Interrupt masked request register

31.1.46 CNT 45

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT45_CTRL	0x40581680	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT45_STATUS	0x40581684	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT45_COUNTER	0x40581688	FULL	Counter count register
TCPWM0_GRP0_CNT45_CC0	0x40581690	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT45_CC0_BUFF	0x40581694	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT45_CC1	0x40581698	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT45_CC1_BUFF	0x4058169C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT45_PERIOD	0x405816A0	FULL	Counter period register
TCPWM0_GRP0_CNT45_PERIOD_BUFF	0x405816A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT45_DT	0x405816B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT45_TR_CMD	0x405816C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT45_TR_IN_SEL0	0x405816C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT45_TR_IN_SEL1	0x405816C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT45_TR_IN_EDGE_SEL	0x405816CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT45_TR_PWM_CTRL	0x405816D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT45_TR_OUT_SEL	0x405816D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT45_INTR	0x405816F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT45_INTR_SET	0x405816F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT45_INTR_MASK	0x405816F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT45_INTR_MASKED	0x405816FC	FULL	Interrupt masked request register

31.1.47 CNT 46

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT46_CTRL	0x40581700	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT46_STATUS	0x40581704	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT46_COUNTER	0x40581708	FULL	Counter count register
TCPWM0_GRP0_CNT46_CC0	0x40581710	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT46_CC0_BUFF	0x40581714	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT46_CC1	0x40581718	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT46_CC1_BUFF	0x4058171C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT46_PERIOD	0x40581720	FULL	Counter period register
TCPWM0_GRP0_CNT46_PERIOD_BUFF	0x40581724	FULL	Counter buffered period register
TCPWM0_GRP0_CNT46_DT	0x40581730	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT46_TR_CMD	0x40581740	FULL	Counter trigger command register
TCPWM0_GRP0_CNT46_TR_IN_SEL0	0x40581744	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT46_TR_IN_SEL1	0x40581748	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT46_TR_IN_EDGE_SEL	0x4058174C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT46_TR_PWM_CTRL	0x40581750	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT46_TR_OUT_SEL	0x40581754	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT46_INTR	0x40581770	FULL	Interrupt request register
TCPWM0_GRP0_CNT46_INTR_SET	0x40581774	FULL	Interrupt set request register
TCPWM0_GRP0_CNT46_INTR_MASK	0x40581778	FULL	Interrupt mask register
TCPWM0_GRP0_CNT46_INTR_MASKED	0x4058177C	FULL	Interrupt masked request register

31.1.48 CNT 47

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT47_CTRL	0x40581780	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT47_STATUS	0x40581784	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT47_COUNTER	0x40581788	FULL	Counter count register
TCPWM0_GRP0_CNT47_CC0	0x40581790	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT47_CC0_BUFF	0x40581794	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT47_CC1	0x40581798	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT47_CC1_BUFF	0x4058179C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT47_PERIOD	0x405817A0	FULL	Counter period register
TCPWM0_GRP0_CNT47_PERIOD_BUFF	0x405817A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT47_DT	0x405817B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT47_TR_CMD	0x405817C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT47_TR_IN_SEL0	0x405817C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT47_TR_IN_SEL1	0x405817C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT47_TR_IN_EDGE_SEL	0x405817CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT47_TR_PWM_CTRL	0x405817D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT47_TR_OUT_SEL	0x405817D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT47_INTR	0x405817F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT47_INTR_SET	0x405817F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT47_INTR_MASK	0x405817F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT47_INTR_MASKED	0x405817FC	FULL	Interrupt masked request register

31.1.49 CNT 48

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT48_CTRL	0x40581800	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT48_STATUS	0x40581804	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT48_COUNTER	0x40581808	FULL	Counter count register
TCPWM0_GRP0_CNT48_CC0	0x40581810	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT48_CC0_BUFF	0x40581814	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT48_CC1	0x40581818	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT48_CC1_BUFF	0x4058181C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT48_PERIOD	0x40581820	FULL	Counter period register
TCPWM0_GRP0_CNT48_PERIOD_BUFF	0x40581824	FULL	Counter buffered period register
TCPWM0_GRP0_CNT48_DT	0x40581830	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT48_TR_CMD	0x40581840	FULL	Counter trigger command register
TCPWM0_GRP0_CNT48_TR_IN_SEL0	0x40581844	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT48_TR_IN_SEL1	0x40581848	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT48_TR_IN_EDGE_SEL	0x4058184C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT48_TR_PWM_CTRL	0x40581850	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT48_TR_OUT_SEL	0x40581854	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT48_INTR	0x40581870	FULL	Interrupt request register
TCPWM0_GRP0_CNT48_INTR_SET	0x40581874	FULL	Interrupt set request register
TCPWM0_GRP0_CNT48_INTR_MASK	0x40581878	FULL	Interrupt mask register
TCPWM0_GRP0_CNT48_INTR_MASKED	0x4058187C	FULL	Interrupt masked request register

31.1.50 CNT 49

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT49_CTRL	0x40581880	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT49_STATUS	0x40581884	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT49_COUNTER	0x40581888	FULL	Counter count register
TCPWM0_GRP0_CNT49_CC0	0x40581890	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT49_CC0_BUFF	0x40581894	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT49_CC1	0x40581898	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT49_CC1_BUFF	0x4058189C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT49_PERIOD	0x405818A0	FULL	Counter period register
TCPWM0_GRP0_CNT49_PERIOD_BUFF	0x405818A4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT49_DT	0x405818B0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT49_TR_CMD	0x405818C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT49_TR_IN_SEL0	0x405818C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT49_TR_IN_SEL1	0x405818C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT49_TR_IN_EDGE_SEL	0x405818CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT49_TR_PWM_CTRL	0x405818D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT49_TR_OUT_SEL	0x405818D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT49_INTR	0x405818F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT49_INTR_SET	0x405818F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT49_INTR_MASK	0x405818F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT49_INTR_MASKED	0x405818FC	FULL	Interrupt masked request register

31.1.51 CNT 50

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT50_CTRL	0x40581900	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT50_STATUS	0x40581904	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT50_COUNTER	0x40581908	FULL	Counter count register
TCPWM0_GRP0_CNT50_CC0	0x40581910	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT50_CC0_BUFF	0x40581914	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT50_CC1	0x40581918	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT50_CC1_BUFF	0x4058191C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT50_PERIOD	0x40581920	FULL	Counter period register
TCPWM0_GRP0_CNT50_PERIOD_BUFF	0x40581924	FULL	Counter buffered period register
TCPWM0_GRP0_CNT50_DT	0x40581930	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT50_TR_CMD	0x40581940	FULL	Counter trigger command register
TCPWM0_GRP0_CNT50_TR_IN_SEL0	0x40581944	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT50_TR_IN_SEL1	0x40581948	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT50_TR_IN_EDGE_SEL	0x4058194C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT50_TR_PWM_CTRL	0x40581950	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT50_TR_OUT_SEL	0x40581954	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT50_INTR	0x40581970	FULL	Interrupt request register
TCPWM0_GRP0_CNT50_INTR_SET	0x40581974	FULL	Interrupt set request register
TCPWM0_GRP0_CNT50_INTR_MASK	0x40581978	FULL	Interrupt mask register
TCPWM0_GRP0_CNT50_INTR_MASKED	0x4058197C	FULL	Interrupt masked request register

31.1.52 CNT 51

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT51_CTRL	0x40581980	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT51_STATUS	0x40581984	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT51_COUNTER	0x40581988	FULL	Counter count register
TCPWM0_GRP0_CNT51_CC0	0x40581990	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT51_CC0_BUFF	0x40581994	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT51_CC1	0x40581998	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT51_CC1_BUFF	0x4058199C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT51_PERIOD	0x405819A0	FULL	Counter period register
TCPWM0_GRP0_CNT51_PERIOD_BUFF	0x405819A4	FULL	Counter buffered period register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT51_DT	0x405819B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT51_TR_CMD	0x405819C0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT51_TR_IN_SEL0	0x405819C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT51_TR_IN_SEL1	0x405819C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT51_TR_IN_EDGE_SEL	0x405819CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT51_TR_PWM_CTRL	0x405819D0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT51_TR_OUT_SEL	0x405819D4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT51_INTR	0x405819F0	FULL	Interrupt request register
TCPWM0_GRP0_CNT51_INTR_SET	0x405819F4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT51_INTR_MASK	0x405819F8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT51_INTR_MASKED	0x405819FC	FULL	Interrupt masked request register

31.1.53 CNT 52

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT52_CTRL	0x40581A00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT52_STATUS	0x40581A04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT52_COUNTER	0x40581A08	FULL	Counter count register
TCPWM0_GRP0_CNT52_CC0	0x40581A10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT52_CC0_BUFF	0x40581A14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT52_CC1	0x40581A18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT52_CC1_BUFF	0x40581A1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT52_PERIOD	0x40581A20	FULL	Counter period register
TCPWM0_GRP0_CNT52_PERIOD_BUFF	0x40581A24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT52_DT	0x40581A30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT52_TR_CMD	0x40581A40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT52_TR_IN_SEL0	0x40581A44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT52_TR_IN_SEL1	0x40581A48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT52_TR_IN_EDGE_SEL	0x40581A4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT52_TR_PWM_CTRL	0x40581A50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT52_TR_OUT_SEL	0x40581A54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT52_INTR	0x40581A70	FULL	Interrupt request register
TCPWM0_GRP0_CNT52_INTR_SET	0x40581A74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT52_INTR_MASK	0x40581A78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT52_INTR_MASKED	0x40581A7C	FULL	Interrupt masked request register

31.1.54 CNT 53

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT53_CTRL	0x40581A80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT53_STATUS	0x40581A84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT53_COUNTER	0x40581A88	FULL	Counter count register
TCPWM0_GRP0_CNT53_CC0	0x40581A90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT53_CC0_BUFF	0x40581A94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT53_CC1	0x40581A98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT53_CC1_BUFF	0x40581A9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT53_PERIOD	0x40581AA0	FULL	Counter period register
TCPWM0_GRP0_CNT53_PERIOD_BUFF	0x40581AA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT53_DT	0x40581AB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT53_TR_CMD	0x40581AC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT53_TR_IN_SEL0	0x40581AC4	FULL	Counter input trigger selection register 0

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT53_TR_IN_SEL1	0x40581AC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT53_TR_IN_EDGE_SEL	0x40581ACC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT53_TR_PWM_CTRL	0x40581AD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT53_TR_OUT_SEL	0x40581AD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT53_INTR	0x40581AF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT53_INTR_SET	0x40581AF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT53_INTR_MASK	0x40581AF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT53_INTR_MASKED	0x40581AFC	FULL	Interrupt masked request register

31.1.55 CNT 54

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT54_CTRL	0x40581B00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT54_STATUS	0x40581B04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT54_COUNTER	0x40581B08	FULL	Counter count register
TCPWM0_GRP0_CNT54_CC0	0x40581B10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT54_CC0_BUFF	0x40581B14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT54_CC1	0x40581B18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT54_CC1_BUFF	0x40581B1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT54_PERIOD	0x40581B20	FULL	Counter period register
TCPWM0_GRP0_CNT54_PERIOD_BUFF	0x40581B24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT54_DT	0x40581B30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT54_TR_CMD	0x40581B40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT54_TR_IN_SEL0	0x40581B44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT54_TR_IN_SEL1	0x40581B48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT54_TR_IN_EDGE_SEL	0x40581B4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT54_TR_PWM_CTRL	0x40581B50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT54_TR_OUT_SEL	0x40581B54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT54_INTR	0x40581B70	FULL	Interrupt request register
TCPWM0_GRP0_CNT54_INTR_SET	0x40581B74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT54_INTR_MASK	0x40581B78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT54_INTR_MASKED	0x40581B7C	FULL	Interrupt masked request register

31.1.56 CNT 55

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT55_CTRL	0x40581B80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT55_STATUS	0x40581B84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT55_COUNTER	0x40581B88	FULL	Counter count register
TCPWM0_GRP0_CNT55_CC0	0x40581B90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT55_CC0_BUFF	0x40581B94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT55_CC1	0x40581B98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT55_CC1_BUFF	0x40581B9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT55_PERIOD	0x40581BA0	FULL	Counter period register
TCPWM0_GRP0_CNT55_PERIOD_BUFF	0x40581BA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT55_DT	0x40581BB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT55_TR_CMD	0x40581BC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT55_TR_IN_SEL0	0x40581BC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT55_TR_IN_SEL1	0x40581BC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT55_TR_IN_EDGE_SEL	0x40581BCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT55_TR_PWM_CTRL	0x40581BD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT55_TR_OUT_SEL	0x40581BD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT55_INTR	0x40581BF0	FULL	Interrupt request register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT55_INTR_SET	0x40581BF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT55_INTR_MASK	0x40581BF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT55_INTR_MASKED	0x40581BFC	FULL	Interrupt masked request register

31.1.57 CNT 56

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT56_CTRL	0x40581C00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT56_STATUS	0x40581C04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT56_COUNTER	0x40581C08	FULL	Counter count register
TCPWM0_GRP0_CNT56_CC0	0x40581C10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT56_CC0_BUFF	0x40581C14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT56_CC1	0x40581C18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT56_CC1_BUFF	0x40581C1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT56_PERIOD	0x40581C20	FULL	Counter period register
TCPWM0_GRP0_CNT56_PERIOD_BUFF	0x40581C24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT56_DT	0x40581C30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT56_TR_CMD	0x40581C40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT56_TR_IN_SEL0	0x40581C44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT56_TR_IN_SEL1	0x40581C48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT56_TR_IN_EDGE_SEL	0x40581C4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT56_TR_PWM_CTRL	0x40581C50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT56_TR_OUT_SEL	0x40581C54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT56_INTR	0x40581C70	FULL	Interrupt request register
TCPWM0_GRP0_CNT56_INTR_SET	0x40581C74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT56_INTR_MASK	0x40581C78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT56_INTR_MASKED	0x40581C7C	FULL	Interrupt masked request register

31.1.58 CNT 57

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT57_CTRL	0x40581C80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT57_STATUS	0x40581C84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT57_COUNTER	0x40581C88	FULL	Counter count register
TCPWM0_GRP0_CNT57_CC0	0x40581C90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT57_CC0_BUFF	0x40581C94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT57_CC1	0x40581C98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT57_CC1_BUFF	0x40581C9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT57_PERIOD	0x40581CA0	FULL	Counter period register
TCPWM0_GRP0_CNT57_PERIOD_BUFF	0x40581CA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT57_DT	0x40581CB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT57_TR_CMD	0x40581CC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT57_TR_IN_SEL0	0x40581CC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT57_TR_IN_SEL1	0x40581CC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT57_TR_IN_EDGE_SEL	0x40581CCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT57_TR_PWM_CTRL	0x40581CD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT57_TR_OUT_SEL	0x40581CD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT57_INTR	0x40581CF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT57_INTR_SET	0x40581CF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT57_INTR_MASK	0x40581CF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT57_INTR_MASKED	0x40581CFC	FULL	Interrupt masked request register

31.1.59 CNT 58

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT58_CTRL	0x40581D00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT58_STATUS	0x40581D04	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT58_COUNTER	0x40581D08	FULL	Counter count register
TCPWM0_GRP0_CNT58_CC0	0x40581D10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT58_CC0_BUFF	0x40581D14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT58_CC1	0x40581D18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT58_CC1_BUFF	0x40581D1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT58_PERIOD	0x40581D20	FULL	Counter period register
TCPWM0_GRP0_CNT58_PERIOD_BUFF	0x40581D24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT58_DT	0x40581D30	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT58_TR_CMD	0x40581D40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT58_TR_IN_SEL0	0x40581D44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT58_TR_IN_SEL1	0x40581D48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT58_TR_IN_EDGE_SEL	0x40581D4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT58_TR_PWM_CTRL	0x40581D50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT58_TR_OUT_SEL	0x40581D54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT58_INTR	0x40581D70	FULL	Interrupt request register
TCPWM0_GRP0_CNT58_INTR_SET	0x40581D74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT58_INTR_MASK	0x40581D78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT58_INTR_MASKED	0x40581D7C	FULL	Interrupt masked request register

31.1.60 CNT 59

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT59_CTRL	0x40581D80	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT59_STATUS	0x40581D84	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT59_COUNTER	0x40581D88	FULL	Counter count register
TCPWM0_GRP0_CNT59_CC0	0x40581D90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT59_CC0_BUFF	0x40581D94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT59_CC1	0x40581D98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT59_CC1_BUFF	0x40581D9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT59_PERIOD	0x40581DA0	FULL	Counter period register
TCPWM0_GRP0_CNT59_PERIOD_BUFF	0x40581DA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT59_DT	0x40581DB0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT59_TR_CMD	0x40581DC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT59_TR_IN_SEL0	0x40581DC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT59_TR_IN_SEL1	0x40581DC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT59_TR_IN_EDGE_SEL	0x40581DCC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT59_TR_PWM_CTRL	0x40581DD0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT59_TR_OUT_SEL	0x40581DD4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT59_INTR	0x40581DF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT59_INTR_SET	0x40581DF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT59_INTR_MASK	0x40581DF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT59_INTR_MASKED	0x40581DFC	FULL	Interrupt masked request register

31.1.61 CNT 60

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT60_CTRL	0x40581E00	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT60_STATUS	0x40581E04	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT60_COUNTER	0x40581E08	FULL	Counter count register
TCPWM0_GRP0_CNT60_CC0	0x40581E10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT60_CC0_BUFF	0x40581E14	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT60_CC1	0x40581E18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT60_CC1_BUFF	0x40581E1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT60_PERIOD	0x40581E20	FULL	Counter period register
TCPWM0_GRP0_CNT60_PERIOD_BUFF	0x40581E24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT60_DT	0x40581E30	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT60_TR_CMD	0x40581E40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT60_TR_IN_SEL0	0x40581E44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT60_TR_IN_SEL1	0x40581E48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT60_TR_IN_EDGE_SEL	0x40581E4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT60_TR_PWM_CTRL	0x40581E50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT60_TR_OUT_SEL	0x40581E54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT60_INTR	0x40581E70	FULL	Interrupt request register
TCPWM0_GRP0_CNT60_INTR_SET	0x40581E74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT60_INTR_MASK	0x40581E78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT60_INTR_MASKED	0x40581E7C	FULL	Interrupt masked request register

31.1.62 CNT 61

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT61_CTRL	0x40581E80	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT61_STATUS	0x40581E84	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT61_COUNTER	0x40581E88	FULL	Counter count register
TCPWM0_GRP0_CNT61_CC0	0x40581E90	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT61_CC0_BUFF	0x40581E94	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP0_CNT61_CC1	0x40581E98	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT61_CC1_BUFF	0x40581E9C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT61_PERIOD	0x40581EA0	FULL	Counter period register
TCPWM0_GRP0_CNT61_PERIOD_BUFF	0x40581EA4	FULL	Counter buffered period register
TCPWM0_GRP0_CNT61_DT	0x40581EB0	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT61_TR_CMD	0x40581EC0	FULL	Counter trigger command register
TCPWM0_GRP0_CNT61_TR_IN_SEL0	0x40581EC4	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT61_TR_IN_SEL1	0x40581EC8	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT61_TR_IN_EDGE_SEL	0x40581ECC	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT61_TR_PWM_CTRL	0x40581ED0	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT61_TR_OUT_SEL	0x40581ED4	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT61_INTR	0x40581EF0	FULL	Interrupt request register
TCPWM0_GRP0_CNT61_INTR_SET	0x40581EF4	FULL	Interrupt set request register
TCPWM0_GRP0_CNT61_INTR_MASK	0x40581EF8	FULL	Interrupt mask register
TCPWM0_GRP0_CNT61_INTR_MASKED	0x40581EFC	FULL	Interrupt masked request register

31.1.63 CNT 62

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT62_CTRL	0x40581F00	FULL	Counter control register Note:AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP0_CNT62_STATUS	0x40581F04	FULL	Counter status register Note:DT_CNT_H is not available for this register
TCPWM0_GRP0_CNT62_COUNTER	0x40581F08	FULL	Counter count register
TCPWM0_GRP0_CNT62_CC0	0x40581F10	FULL	Counter compare/capture 0 register
TCPWM0_GRP0_CNT62_CC0_BUFF	0x40581F14	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP0_CNT62_CC1	0x40581F18	FULL	Counter compare/capture 1 register
TCPWM0_GRP0_CNT62_CC1_BUFF	0x40581F1C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP0_CNT62_PERIOD	0x40581F20	FULL	Counter period register
TCPWM0_GRP0_CNT62_PERIOD_BUFF	0x40581F24	FULL	Counter buffered period register
TCPWM0_GRP0_CNT62_DT	0x40581F30	FULL	Counter PWM dead time register Note:DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP0_CNT62_TR_CMD	0x40581F40	FULL	Counter trigger command register
TCPWM0_GRP0_CNT62_TR_IN_SEL0	0x40581F44	FULL	Counter input trigger selection register 0
TCPWM0_GRP0_CNT62_TR_IN_SEL1	0x40581F48	FULL	Counter input trigger selection register 1
TCPWM0_GRP0_CNT62_TR_IN_EDGE_SEL	0x40581F4C	FULL	Counter input trigger edge selection register
TCPWM0_GRP0_CNT62_TR_PWM_CTRL	0x40581F50	FULL	Counter trigger PWM control register
TCPWM0_GRP0_CNT62_TR_OUT_SEL	0x40581F54	FULL	Counter output trigger selection register
TCPWM0_GRP0_CNT62_INTR	0x40581F70	FULL	Interrupt request register
TCPWM0_GRP0_CNT62_INTR_SET	0x40581F74	FULL	Interrupt set request register
TCPWM0_GRP0_CNT62_INTR_MASK	0x40581F78	FULL	Interrupt mask register
TCPWM0_GRP0_CNT62_INTR_MASKED	0x40581F7C	FULL	Interrupt masked request register

31.2 GRP 1

31.2.1 CNT 0

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT0_CTRL	0x40588000	FULL	Counter control register
TCPWM0_GRP1_CNT0_STATUS	0x40588004	FULL	Counter status register
TCPWM0_GRP1_CNT0_COUNTER	0x40588008	FULL	Counter count register
TCPWM0_GRP1_CNT0_CC0	0x40588010	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT0_CC0_BUFF	0x40588014	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT0_CC1	0x40588018	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT0_CC1_BUFF	0x4058801C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT0_PERIOD	0x40588020	FULL	Counter period register
TCPWM0_GRP1_CNT0_PERIOD_BUFF	0x40588024	FULL	Counter buffered period register
TCPWM0_GRP1_CNT0_LINE_SEL	0x40588028	FULL	Counter line selection register
TCPWM0_GRP1_CNT0_LINE_SEL_BUFF	0x4058802C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT0_DT	0x40588030	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT0_TR_CMD	0x40588040	FULL	Counter trigger command register
TCPWM0_GRP1_CNT0_TR_IN_SEL0	0x40588044	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT0_TR_IN_SEL1	0x40588048	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT0_TR_IN_EDGE_SEL	0x4058804C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT0_TR_PWM_CTRL	0x40588050	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT0_TR_OUT_SEL	0x40588054	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT0_INTR	0x40588070	FULL	Interrupt request register
TCPWM0_GRP1_CNT0_INTR_SET	0x40588074	FULL	Interrupt set request register
TCPWM0_GRP1_CNT0_INTR_MASK	0x40588078	FULL	Interrupt mask register
TCPWM0_GRP1_CNT0_INTR_MASKED	0x4058807C	FULL	Interrupt masked request register

31.2.2 CNT 1

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT1_CTRL	0x40588080	FULL	Counter control register
TCPWM0_GRP1_CNT1_STATUS	0x40588084	FULL	Counter status register
TCPWM0_GRP1_CNT1_COUNTER	0x40588088	FULL	Counter count register
TCPWM0_GRP1_CNT1_CC0	0x40588090	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT1_CC0_BUFF	0x40588094	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT1_CC1	0x40588098	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT1_CC1_BUFF	0x4058809C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT1_PERIOD	0x405880A0	FULL	Counter period register
TCPWM0_GRP1_CNT1_PERIOD_BUFF	0x405880A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT1_LINE_SEL	0x405880A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT1_LINE_SEL_BUFF	0x405880AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT1_DT	0x405880B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT1_TR_CMD	0x405880C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT1_TR_IN_SEL0	0x405880C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT1_TR_IN_SEL1	0x405880C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT1_TR_IN_EDGE_SEL	0x405880CC	FULL	Counter input trigger edge selection register

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT1_TR_PWM_CTRL	0x405880D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT1_TR_OUT_SEL	0x405880D4	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT1_INTR	0x405880F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT1_INTR_SET	0x405880F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT1_INTR_MASK	0x405880F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT1_INTR_MASKED	0x405880FC	FULL	Interrupt masked request register

31.2.3 CNT 2

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT2_CTRL	0x40588100	FULL	Counter control register
TCPWM0_GRP1_CNT2_STATUS	0x40588104	FULL	Counter status register
TCPWM0_GRP1_CNT2_COUNTER	0x40588108	FULL	Counter count register
TCPWM0_GRP1_CNT2_CC0	0x40588110	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT2_CC0_BUFF	0x40588114	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT2_CC1	0x40588118	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT2_CC1_BUFF	0x4058811C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT2_PERIOD	0x40588120	FULL	Counter period register
TCPWM0_GRP1_CNT2_PERIOD_BUFF	0x40588124	FULL	Counter buffered period register
TCPWM0_GRP1_CNT2_LINE_SEL	0x40588128	FULL	Counter line selection register
TCPWM0_GRP1_CNT2_LINE_SEL_BUFF	0x4058812C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT2_DT	0x40588130	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT2_TR_CMD	0x40588140	FULL	Counter trigger command register
TCPWM0_GRP1_CNT2_TR_IN_SEL0	0x40588144	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT2_TR_IN_SEL1	0x40588148	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT2_TR_IN_EDGE_SEL	0x4058814C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT2_TR_PWM_CTRL	0x40588150	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT2_TR_OUT_SEL	0x40588154	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT2_INTR	0x40588170	FULL	Interrupt request register
TCPWM0_GRP1_CNT2_INTR_SET	0x40588174	FULL	Interrupt set request register
TCPWM0_GRP1_CNT2_INTR_MASK	0x40588178	FULL	Interrupt mask register
TCPWM0_GRP1_CNT2_INTR_MASKED	0x4058817C	FULL	Interrupt masked request register

31.2.4 CNT 3

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT3_CTRL	0x40588180	FULL	Counter control register
TCPWM0_GRP1_CNT3_STATUS	0x40588184	FULL	Counter status register
TCPWM0_GRP1_CNT3_COUNTER	0x40588188	FULL	Counter count register
TCPWM0_GRP1_CNT3_CC0	0x40588190	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT3_CC0_BUFF	0x40588194	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT3_CC1	0x40588198	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT3_CC1_BUFF	0x4058819C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT3_PERIOD	0x405881A0	FULL	Counter period register
TCPWM0_GRP1_CNT3_PERIOD_BUFF	0x405881A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT3_LINE_SEL	0x405881A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT3_LINE_SEL_BUFF	0x405881AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT3_DT	0x405881B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT3_TR_CMD	0x405881C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT3_TR_IN_SEL0	0x405881C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT3_TR_IN_SEL1	0x405881C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT3_TR_IN_EDGE_SEL	0x405881CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT3_TR_PWM_CTRL	0x405881D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT3_TR_OUT_SEL	0x405881D4	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT3_INTR	0x405881F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT3_INTR_SET	0x405881F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT3_INTR_MASK	0x405881F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT3_INTR_MASKED	0x405881FC	FULL	Interrupt masked request register

31.2.5 CNT 4

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT4_CTRL	0x40588200	FULL	Counter control register
TCPWM0_GRP1_CNT4_STATUS	0x40588204	FULL	Counter status register
TCPWM0_GRP1_CNT4_COUNTER	0x40588208	FULL	Counter count register
TCPWM0_GRP1_CNT4_CC0	0x40588210	FULL	Counter compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT4_CC0_BUFF	0x40588214	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT4_CC1	0x40588218	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT4_CC1_BUFF	0x4058821C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT4_PERIOD	0x40588220	FULL	Counter period register
TCPWM0_GRP1_CNT4_PERIOD_BUFF	0x40588224	FULL	Counter buffered period register
TCPWM0_GRP1_CNT4_LINE_SEL	0x40588228	FULL	Counter line selection register
TCPWM0_GRP1_CNT4_LINE_SEL_BUFF	0x4058822C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT4_DT	0x40588230	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT4_TR_CMD	0x40588240	FULL	Counter trigger command register
TCPWM0_GRP1_CNT4_TR_IN_SEL0	0x40588244	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT4_TR_IN_SEL1	0x40588248	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT4_TR_IN_EDGE_SEL	0x4058824C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT4_TR_PWM_CTRL	0x40588250	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT4_TR_OUT_SEL	0x40588254	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT4_INTR	0x40588270	FULL	Interrupt request register
TCPWM0_GRP1_CNT4_INTR_SET	0x40588274	FULL	Interrupt set request register
TCPWM0_GRP1_CNT4_INTR_MASK	0x40588278	FULL	Interrupt mask register
TCPWM0_GRP1_CNT4_INTR_MASKED	0x4058827C	FULL	Interrupt masked request register

31.2.6 CNT 5

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT5_CTRL	0x40588280	FULL	Counter control register
TCPWM0_GRP1_CNT5_STATUS	0x40588284	FULL	Counter status register
TCPWM0_GRP1_CNT5_COUNTER	0x40588288	FULL	Counter count register
TCPWM0_GRP1_CNT5_CC0	0x40588290	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT5_CC0_BUFF	0x40588294	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT5_CC1	0x40588298	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT5_CC1_BUFF	0x4058829C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT5_PERIOD	0x405882A0	FULL	Counter period register
TCPWM0_GRP1_CNT5_PERIOD_BUFF	0x405882A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT5_LINE_SEL	0x405882A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT5_LINE_SEL_BUFF	0x405882AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT5_DT	0x405882B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT5_TR_CMD	0x405882C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT5_TR_IN_SEL0	0x405882C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT5_TR_IN_SEL1	0x405882C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT5_TR_IN_EDGE_SEL	0x405882CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT5_TR_PWM_CTRL	0x405882D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT5_TR_OUT_SEL	0x405882D4	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT5_INTR	0x405882F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT5_INTR_SET	0x405882F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT5_INTR_MASK	0x405882F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT5_INTR_MASKED	0x405882FC	FULL	Interrupt masked request register

31.2.7 CNT 6

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT6_CTRL	0x40588300	FULL	Counter control register
TCPWM0_GRP1_CNT6_STATUS	0x40588304	FULL	Counter status register
TCPWM0_GRP1_CNT6_COUNTER	0x40588308	FULL	Counter count register
TCPWM0_GRP1_CNT6_CC0	0x40588310	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT6_CC0_BUFF	0x40588314	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT6_CC1	0x40588318	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT6_CC1_BUFF	0x4058831C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT6_PERIOD	0x40588320	FULL	Counter period register
TCPWM0_GRP1_CNT6_PERIOD_BUFF	0x40588324	FULL	Counter buffered period register
TCPWM0_GRP1_CNT6_LINE_SEL	0x40588328	FULL	Counter line selection register
TCPWM0_GRP1_CNT6_LINE_SEL_BUFF	0x4058832C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT6_DT	0x40588330	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT6_TR_CMD	0x40588340	FULL	Counter trigger command register
TCPWM0_GRP1_CNT6_TR_IN_SEL0	0x40588344	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT6_TR_IN_SEL1	0x40588348	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT6_TR_IN_EDGE_SEL	0x4058834C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT6_TR_PWM_CTRL	0x40588350	FULL	Counter trigger PWM control register

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT6_TR_OUT_SEL	0x40588354	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT6_INTR	0x40588370	FULL	Interrupt request register
TCPWM0_GRP1_CNT6_INTR_SET	0x40588374	FULL	Interrupt set request register
TCPWM0_GRP1_CNT6_INTR_MASK	0x40588378	FULL	Interrupt mask register
TCPWM0_GRP1_CNT6_INTR_MASKED	0x4058837C	FULL	Interrupt masked request register

31.2.8 CNT 7

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT7_CTRL	0x40588380	FULL	Counter control register
TCPWM0_GRP1_CNT7_STATUS	0x40588384	FULL	Counter status register
TCPWM0_GRP1_CNT7_COUNTER	0x40588388	FULL	Counter count register
TCPWM0_GRP1_CNT7_CC0	0x40588390	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT7_CC0_BUFF	0x40588394	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT7_CC1	0x40588398	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT7_CC1_BUFF	0x4058839C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT7_PERIOD	0x405883A0	FULL	Counter period register
TCPWM0_GRP1_CNT7_PERIOD_BUFF	0x405883A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT7_LINE_SEL	0x405883A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT7_LINE_SEL_BUFF	0x405883AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT7_DT	0x405883B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT7_TR_CMD	0x405883C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT7_TR_IN_SEL0	0x405883C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT7_TR_IN_SEL1	0x405883C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT7_TR_IN_EDGE_SEL	0x405883CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT7_TR_PWM_CTRL	0x405883D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT7_TR_OUT_SEL	0x405883D4	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT7_INTR	0x405883F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT7_INTR_SET	0x405883F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT7_INTR_MASK	0x405883F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT7_INTR_MASKED	0x405883FC	FULL	Interrupt masked request register

31.2.9 CNT 8

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT8_CTRL	0x40588400	FULL	Counter control register
TCPWM0_GRP1_CNT8_STATUS	0x40588404	FULL	Counter status register
TCPWM0_GRP1_CNT8_COUNTER	0x40588408	FULL	Counter count register
TCPWM0_GRP1_CNT8_CC0	0x40588410	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT8_CC0_BUFF	0x40588414	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT8_CC1	0x40588418	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT8_CC1_BUFF	0x4058841C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT8_PERIOD	0x40588420	FULL	Counter period register
TCPWM0_GRP1_CNT8_PERIOD_BUFF	0x40588424	FULL	Counter buffered period register
TCPWM0_GRP1_CNT8_LINE_SEL	0x40588428	FULL	Counter line selection register
TCPWM0_GRP1_CNT8_LINE_SEL_BUFF	0x4058842C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT8_DT	0x40588430	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT8_TR_CMD	0x40588440	FULL	Counter trigger command register
TCPWM0_GRP1_CNT8_TR_IN_SEL0	0x40588444	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT8_TR_IN_SEL1	0x40588448	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT8_TR_IN_EDGE_SEL	0x4058844C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT8_TR_PWM_CTRL	0x40588450	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT8_TR_OUT_SEL	0x40588454	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT8_INTR	0x40588470	FULL	Interrupt request register
TCPWM0_GRP1_CNT8_INTR_SET	0x40588474	FULL	Interrupt set request register
TCPWM0_GRP1_CNT8_INTR_MASK	0x40588478	FULL	Interrupt mask register
TCPWM0_GRP1_CNT8_INTR_MASKED	0x4058847C	FULL	Interrupt masked request register

31.2.10 CNT 9

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT9_CTRL	0x40588480	FULL	Counter control register
TCPWM0_GRP1_CNT9_STATUS	0x40588484	FULL	Counter status register
TCPWM0_GRP1_CNT9_COUNTER	0x40588488	FULL	Counter count register
TCPWM0_GRP1_CNT9_CC0	0x40588490	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT9_CC0_BUFF	0x40588494	FULL	Counter buffered compare/capture 0 register

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT9_CC1	0x40588498	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT9_CC1_BUFF	0x4058849C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT9_PERIOD	0x405884A0	FULL	Counter period register
TCPWM0_GRP1_CNT9_PERIOD_BUFF	0x405884A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT9_LINE_SEL	0x405884A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT9_LINE_SEL_BUFF	0x405884AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT9_DT	0x405884B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT9_TR_CMD	0x405884C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT9_TR_IN_SEL0	0x405884C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT9_TR_IN_SEL1	0x405884C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT9_TR_IN_EDGE_SEL	0x405884CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT9_TR_PWM_CTRL	0x405884D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT9_TR_OUT_SEL	0x405884D4	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT9_INTR	0x405884F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT9_INTR_SET	0x405884F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT9_INTR_MASK	0x405884F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT9_INTR_MASKED	0x405884FC	FULL	Interrupt masked request register

31.2.11 CNT 10

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT10_CTRL	0x40588500	FULL	Counter control register
TCPWM0_GRP1_CNT10_STATUS	0x40588504	FULL	Counter status register
TCPWM0_GRP1_CNT10_COUNTER	0x40588508	FULL	Counter count register
TCPWM0_GRP1_CNT10_CC0	0x40588510	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT10_CC0_BUFF	0x40588514	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT10_CC1	0x40588518	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT10_CC1_BUFF	0x4058851C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT10_PERIOD	0x40588520	FULL	Counter period register
TCPWM0_GRP1_CNT10_PERIOD_BUFF	0x40588524	FULL	Counter buffered period register
TCPWM0_GRP1_CNT10_LINE_SEL	0x40588528	FULL	Counter line selection register
TCPWM0_GRP1_CNT10_LINE_SEL_BUFF	0x4058852C	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT10_DT	0x40588530	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT10_TR_CMD	0x40588540	FULL	Counter trigger command register
TCPWM0_GRP1_CNT10_TR_IN_SEL0	0x40588544	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT10_TR_IN_SEL1	0x40588548	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT10_TR_IN_EDGE_SEL	0x4058854C	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT10_TR_PWM_CTRL	0x40588550	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT10_TR_OUT_SEL	0x40588554	FULL	Counter output trigger selection register
TCPWM0_GRP1_CNT10_INTR	0x40588570	FULL	Interrupt request register
TCPWM0_GRP1_CNT10_INTR_SET	0x40588574	FULL	Interrupt set request register
TCPWM0_GRP1_CNT10_INTR_MASK	0x40588578	FULL	Interrupt mask register
TCPWM0_GRP1_CNT10_INTR_MASKED	0x4058857C	FULL	Interrupt masked request register

31.2.12 CNT 11

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT11_CTRL	0x40588580	FULL	Counter control register
TCPWM0_GRP1_CNT11_STATUS	0x40588584	FULL	Counter status register
TCPWM0_GRP1_CNT11_COUNTER	0x40588588	FULL	Counter count register
TCPWM0_GRP1_CNT11_CC0	0x40588590	FULL	Counter compare/capture 0 register
TCPWM0_GRP1_CNT11_CC0_BUFF	0x40588594	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP1_CNT11_CC1	0x40588598	FULL	Counter compare/capture 1 register
TCPWM0_GRP1_CNT11_CC1_BUFF	0x4058859C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP1_CNT11_PERIOD	0x405885A0	FULL	Counter period register
TCPWM0_GRP1_CNT11_PERIOD_BUFF	0x405885A4	FULL	Counter buffered period register
TCPWM0_GRP1_CNT11_LINE_SEL	0x405885A8	FULL	Counter line selection register
TCPWM0_GRP1_CNT11_LINE_SEL_BUFF	0x405885AC	FULL	Counter buffered line selection register
TCPWM0_GRP1_CNT11_DT	0x405885B0	FULL	Counter PWM dead time register
TCPWM0_GRP1_CNT11_TR_CMD	0x405885C0	FULL	Counter trigger command register
TCPWM0_GRP1_CNT11_TR_IN_SEL0	0x405885C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP1_CNT11_TR_IN_SEL1	0x405885C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP1_CNT11_TR_IN_EDGE_SEL	0x405885CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP1_CNT11_TR_PWM_CTRL	0x405885D0	FULL	Counter trigger PWM control register
TCPWM0_GRP1_CNT11_TR_OUT_SEL	0x405885D4	FULL	Counter output trigger selection register

Register Name	Address	Permission	Description
TCPWM0_GRP1_CNT11_INTR	0x405885F0	FULL	Interrupt request register
TCPWM0_GRP1_CNT11_INTR_SET	0x405885F4	FULL	Interrupt set request register
TCPWM0_GRP1_CNT11_INTR_MASK	0x405885F8	FULL	Interrupt mask register
TCPWM0_GRP1_CNT11_INTR_MASKED	0x405885FC	FULL	Interrupt masked request register

31.3 GRP 2

31.3.1 CNT 0

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT0_CTRL	0x40590000	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT0_STATUS	0x40590004	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT0_COUNTER	0x40590008	FULL	Counter count register
TCPWM0_GRP2_CNT0_CC0	0x40590010	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT0_CC0_BUFF	0x40590014	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT0_CC1	0x40590018	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT0_CC1_BUFF	0x4059001C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT0_PERIOD	0x40590020	FULL	Counter period register
TCPWM0_GRP2_CNT0_PERIOD_BUFF	0x40590024	FULL	Counter buffered period register
TCPWM0_GRP2_CNT0_DT	0x40590030	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT0_TR_CMD	0x40590040	FULL	Counter trigger command register
TCPWM0_GRP2_CNT0_TR_IN_SEL0	0x40590044	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT0_TR_IN_SEL1	0x40590048	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT0_TR_IN_EDGE_SEL	0x4059004C	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT0_TR_PWM_CTRL	0x40590050	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT0_TR_OUT_SEL	0x40590054	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT0_INTR	0x40590070	FULL	Interrupt request register
TCPWM0_GRP2_CNT0_INTR_SET	0x40590074	FULL	Interrupt set request register
TCPWM0_GRP2_CNT0_INTR_MASK	0x40590078	FULL	Interrupt mask register
TCPWM0_GRP2_CNT0_INTR_MASKED	0x4059007C	FULL	Interrupt masked request register

31.3.2 CNT 1

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT1_CTRL	0x40590080	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT1_STATUS	0x40590084	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT1_COUNTER	0x40590088	FULL	Counter count register
TCPWM0_GRP2_CNT1_CC0	0x40590090	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT1_CC0_BUFF	0x40590094	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT1_CC1	0x40590098	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT1_CC1_BUFF	0x4059009C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT1_PERIOD	0x405900A0	FULL	Counter period register
TCPWM0_GRP2_CNT1_PERIOD_BUFF	0x405900A4	FULL	Counter buffered period register
TCPWM0_GRP2_CNT1_DT	0x405900B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT1_TR_CMD	0x405900C0	FULL	Counter trigger command register
TCPWM0_GRP2_CNT1_TR_IN_SEL0	0x405900C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT1_TR_IN_SEL1	0x405900C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT1_TR_IN_EDGE_SEL	0x405900CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT1_TR_PWM_CTRL	0x405900D0	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT1_TR_OUT_SEL	0x405900D4	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT1_INTR	0x405900F0	FULL	Interrupt request register
TCPWM0_GRP2_CNT1_INTR_SET	0x405900F4	FULL	Interrupt set request register
TCPWM0_GRP2_CNT1_INTR_MASK	0x405900F8	FULL	Interrupt mask register

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT1_INTR_MASKED	0x405900FC	FULL	Interrupt masked request register

31.3.3 CNT 2

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT2_CTRL	0x40590100	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT2_STATUS	0x40590104	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT2_COUNTER	0x40590108	FULL	Counter count register
TCPWM0_GRP2_CNT2_CC0	0x40590110	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT2_CC0_BUFF	0x40590114	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT2_CC1	0x40590118	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT2_CC1_BUFF	0x4059011C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT2_PERIOD	0x40590120	FULL	Counter period register
TCPWM0_GRP2_CNT2_PERIOD_BUFF	0x40590124	FULL	Counter buffered period register
TCPWM0_GRP2_CNT2_DT	0x40590130	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT2_TR_CMD	0x40590140	FULL	Counter trigger command register
TCPWM0_GRP2_CNT2_TR_IN_SEL0	0x40590144	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT2_TR_IN_SEL1	0x40590148	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT2_TR_IN_EDGE_SEL	0x4059014C	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT2_TR_PWM_CTRL	0x40590150	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT2_TR_OUT_SEL	0x40590154	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT2_INTR	0x40590170	FULL	Interrupt request register
TCPWM0_GRP2_CNT2_INTR_SET	0x40590174	FULL	Interrupt set request register
TCPWM0_GRP2_CNT2_INTR_MASK	0x40590178	FULL	Interrupt mask register
TCPWM0_GRP2_CNT2_INTR_MASKED	0x4059017C	FULL	Interrupt masked request register

31.3.4 CNT 3

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT3_CTRL	0x40590180	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT3_STATUS	0x40590184	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT3_COUNTER	0x40590188	FULL	Counter count register
TCPWM0_GRP2_CNT3_CC0	0x40590190	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT3_CC0_BUFF	0x40590194	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT3_CC1	0x40590198	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT3_CC1_BUFF	0x4059019C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT3_PERIOD	0x405901A0	FULL	Counter period register
TCPWM0_GRP2_CNT3_PERIOD_BUFF	0x405901A4	FULL	Counter buffered period register
TCPWM0_GRP2_CNT3_DT	0x405901B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT3_TR_CMD	0x405901C0	FULL	Counter trigger command register
TCPWM0_GRP2_CNT3_TR_IN_SEL0	0x405901C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT3_TR_IN_SEL1	0x405901C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT3_TR_IN_EDGE_SEL	0x405901CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT3_TR_PWM_CTRL	0x405901D0	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT3_TR_OUT_SEL	0x405901D4	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT3_INTR	0x405901F0	FULL	Interrupt request register
TCPWM0_GRP2_CNT3_INTR_SET	0x405901F4	FULL	Interrupt set request register
TCPWM0_GRP2_CNT3_INTR_MASK	0x405901F8	FULL	Interrupt mask register
TCPWM0_GRP2_CNT3_INTR_MASKED	0x405901FC	FULL	Interrupt masked request register

31.3.5 CNT 4

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT4_CTRL	0x40590200	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT4_STATUS	0x40590204	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT4_COUNTER	0x40590208	FULL	Counter count register
TCPWM0_GRP2_CNT4_CC0	0x40590210	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT4_CC0_BUFF	0x40590214	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT4_CC1	0x40590218	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT4_CC1_BUFF	0x4059021C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT4_PERIOD	0x40590220	FULL	Counter period register
TCPWM0_GRP2_CNT4_PERIOD_BUFF	0x40590224	FULL	Counter buffered period register
TCPWM0_GRP2_CNT4_DT	0x40590230	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT4_TR_CMD	0x40590240	FULL	Counter trigger command register
TCPWM0_GRP2_CNT4_TR_IN_SEL0	0x40590244	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT4_TR_IN_SEL1	0x40590248	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT4_TR_IN_EDGE_SEL	0x4059024C	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT4_TR_PWM_CTRL	0x40590250	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT4_TR_OUT_SEL	0x40590254	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT4_INTR	0x40590270	FULL	Interrupt request register
TCPWM0_GRP2_CNT4_INTR_SET	0x40590274	FULL	Interrupt set request register
TCPWM0_GRP2_CNT4_INTR_MASK	0x40590278	FULL	Interrupt mask register
TCPWM0_GRP2_CNT4_INTR_MASKED	0x4059027C	FULL	Interrupt masked request register

31.3.6 CNT 5

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT5_CTRL	0x40590280	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT5_STATUS	0x40590284	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT5_COUNTER	0x40590288	FULL	Counter count register
TCPWM0_GRP2_CNT5_CC0	0x40590290	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT5_CC0_BUFF	0x40590294	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT5_CC1	0x40590298	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT5_CC1_BUFF	0x4059029C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT5_PERIOD	0x405902A0	FULL	Counter period register
TCPWM0_GRP2_CNT5_PERIOD_BUFF	0x405902A4	FULL	Counter buffered period register
TCPWM0_GRP2_CNT5_DT	0x405902B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT5_TR_CMD	0x405902C0	FULL	Counter trigger command register
TCPWM0_GRP2_CNT5_TR_IN_SEL0	0x405902C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT5_TR_IN_SEL1	0x405902C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT5_TR_IN_EDGE_SEL	0x405902CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT5_TR_PWM_CTRL	0x405902D0	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT5_TR_OUT_SEL	0x405902D4	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT5_INTR	0x405902F0	FULL	Interrupt request register
TCPWM0_GRP2_CNT5_INTR_SET	0x405902F4	FULL	Interrupt set request register
TCPWM0_GRP2_CNT5_INTR_MASK	0x405902F8	FULL	Interrupt mask register
TCPWM0_GRP2_CNT5_INTR_MASKED	0x405902FC	FULL	Interrupt masked request register

31.3.7 CNT 6

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT6_CTRL	0x40590300	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT6_STATUS	0x40590304	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT6_COUNTER	0x40590308	FULL	Counter count register
TCPWM0_GRP2_CNT6_CC0	0x40590310	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT6_CC0_BUFF	0x40590314	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT6_CC1	0x40590318	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT6_CC1_BUFF	0x4059031C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT6_PERIOD	0x40590320	FULL	Counter period register
TCPWM0_GRP2_CNT6_PERIOD_BUFF	0x40590324	FULL	Counter buffered period register
TCPWM0_GRP2_CNT6_DT	0x40590330	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT6_TR_CMD	0x40590340	FULL	Counter trigger command register
TCPWM0_GRP2_CNT6_TR_IN_SEL0	0x40590344	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT6_TR_IN_SEL1	0x40590348	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT6_TR_IN_EDGE_SEL	0x4059034C	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT6_TR_PWM_CTRL	0x40590350	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT6_TR_OUT_SEL	0x40590354	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT6_INTR	0x40590370	FULL	Interrupt request register
TCPWM0_GRP2_CNT6_INTR_SET	0x40590374	FULL	Interrupt set request register
TCPWM0_GRP2_CNT6_INTR_MASK	0x40590378	FULL	Interrupt mask register
TCPWM0_GRP2_CNT6_INTR_MASKED	0x4059037C	FULL	Interrupt masked request register

31.3.8 CNT 7

Register Name	Address	Permission	Description
TCPWM0_GRP2_CNT7_CTRL	0x40590380	FULL	Counter control register Note: AUTO_RELOAD_LINE_SEL CC0_MATCH_UP_EN CC0_MATCH_DOWN_EN CC1_MATCH_UP_EN CC1_MATCH_DOWN_EN are not available for this register
TCPWM0_GRP2_CNT7_STATUS	0x40590384	FULL	Counter status register Note: DT_CNT_H is not available for this register
TCPWM0_GRP2_CNT7_COUNTER	0x40590388	FULL	Counter count register
TCPWM0_GRP2_CNT7_CC0	0x40590390	FULL	Counter compare/capture 0 register
TCPWM0_GRP2_CNT7_CC0_BUFF	0x40590394	FULL	Counter buffered compare/capture 0 register
TCPWM0_GRP2_CNT7_CC1	0x40590398	FULL	Counter compare/capture 1 register
TCPWM0_GRP2_CNT7_CC1_BUFF	0x4059039C	FULL	Counter buffered compare/capture 1 register
TCPWM0_GRP2_CNT7_PERIOD	0x405903A0	FULL	Counter period register
TCPWM0_GRP2_CNT7_PERIOD_BUFF	0x405903A4	FULL	Counter buffered period register
TCPWM0_GRP2_CNT7_DT	0x405903B0	FULL	Counter PWM dead time register Note: DT_LINE_OUT_H DT_LINE_COMPL_OUT are not available for this register
TCPWM0_GRP2_CNT7_TR_CMD	0x405903C0	FULL	Counter trigger command register
TCPWM0_GRP2_CNT7_TR_IN_SEL0	0x405903C4	FULL	Counter input trigger selection register 0
TCPWM0_GRP2_CNT7_TR_IN_SEL1	0x405903C8	FULL	Counter input trigger selection register 1
TCPWM0_GRP2_CNT7_TR_IN_EDGE_SEL	0x405903CC	FULL	Counter input trigger edge selection register
TCPWM0_GRP2_CNT7_TR_PWM_CTRL	0x405903D0	FULL	Counter trigger PWM control register
TCPWM0_GRP2_CNT7_TR_OUT_SEL	0x405903D4	FULL	Counter output trigger selection register
TCPWM0_GRP2_CNT7_INTR	0x405903F0	FULL	Interrupt request register
TCPWM0_GRP2_CNT7_INTR_SET	0x405903F4	FULL	Interrupt set request register
TCPWM0_GRP2_CNT7_INTR_MASK	0x405903F8	FULL	Interrupt mask register
TCPWM0_GRP2_CNT7_INTR_MASKED	0x405903FC	FULL	Interrupt masked request register

31.4 Register Details

31.4.1 GRP

31.4.1.1 CNT

31.4.1.1.1 TCPWM_GRP_CNT_CTRL

Description: Counter control register
Address: 0x40580000
Offset: 0x0
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xF0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC1 _MATCH _DOWN _EN [7:7]	CC1 _MATCH _UP_EN [6:6]	CC0 _MATCH _DOWN _EN [5:5]	CC0 _MATCH _UP_EN [4:4]	AUTO _RELOAD _LINE_SEL [3:3]	AUTO _RELOAD _PERIOD [2:2]	AUTO _RELOAD _CC1 [1:1]	AUTO _RELOAD _CC0 [0:0]
Bits	15	14	13	12	11	10	9	8
Name	None [15:14]		PWM_DISABLE_MODE [13:12]		None [11:11]	PWM _SYNC_ KILL [10:10]	PWM _STOP_ON _KILL [9:9]	PWM_IMM _KILL [8:8]
Bits	23	22	21	20	19	18	17	16
Name	None [23:22]		QUAD_ENCODING _MODE [21:20]		None [19:19]	ONE _SHOT [18:18]	UP_DOWN_MODE [17:16]	
Bits	31	30	29	28	27	26	25	24
Name	ENABLED [31:31]	DBG _FREEZE _EN [30:30]	None [29:27]			MODE [26:24]		

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	AUTO_RELOAD_CC0	RW	RW	0	Specifies switching of the CC0 and buffered CC0 values. This field has a function in TIMER, QUAD (QUAD_RANGE0_CMP, QUAD_RANGE1_CMP range modes), SR, PWM, PWM_DT and PWM_PR modes. Timer, QUAD, SR modes: '0': never switch. '1': switch on a compare match 0 event. PWM, PWM_DT, PWM_PR modes: '0': never switch. '1': switch on a terminal count event with an actively pending switch event.

Bits	Name	SW	HW	Default or Enum	Description
1	AUTO_RELOAD_CC1	RW	RW	0	Specifies switching of the CC1 and buffered CC1 values. This field has a function in TIMER, QUAD (QUAD_RANGE0_CMP, QUAD_RANGE1_CMP range modes), SR, PWM, PWM_DT and PWM_PR modes. Timer, QUAD, SR modes: '0': never switch. '1': switch on a compare match 1 event. PWM, PWM_DT, PWM_PR modes: '0': never switch. '1': switch on a terminal count event with an actively pending switch event.
2	AUTO_RELOAD_PERIOD	RW	RW	0	Specifies switching of the PERIOD and buffered PERIOD values. This field has a function in PWM and PWM_DT modes. '0': never switch. '1': switch on a terminal count event with and actively pending switch event. In QUAD mode, QUAD_RANGE0_CMP range mode this field is used to select the index / wrap-around capture function. '0': Captures on index (reload) event. The counter value is copied to the PERIOD register on an index (reload) event. '1': Captures when COUNTER equals 0 or 0xffff. The counter value is copied to the PERIOD register when COUNTER equals 0 or 0xffff.
3	AUTO_RELOAD_LINE_SEL	RW	RW	0	Specifies switching of the LINE_SEL and LINE_BUFF_SEL values. This field has a function in PWM and PWM_PR modes. '0': never switch. '1': switch on a terminal count event with and actively pending switch event.
4	CC0_MATCH_UP_EN	RW	RW	1	Enables / disables the compare match 0 event generation (COUNTER equals CC0 register) when counting up (STATUS.DOWN = 0) in CNT_UPDN1/2 mode. '0': compare match 0 event generation disabled when counting up '1': compare match 0 event generation enabled when counting up This field has a function in PWM and PWM_DT modes only.
5	CC0_MATCH_DOWN_EN	RW	RW	1	Enables / disables the compare match 0 event generation (COUNTER equals CC0 register) when counting down (STATUS.DOWN = 1) in CNT_UPDN1/2 mode. '0': compare match 0 event generation disabled when counting down '1': compare match 0 event generation enabled when counting down This field has a function in PWM and PWM_DT modes only.

Bits	Name	SW	HW	Default or Enum	Description
6	CC1_MATCH_UP_EN	RW	RW	1	Enables / disables the compare match 1 event generation (COUNTER equals CC0 register) when counting up (STATUS.DOWN = 0) in CNT_UPDN1/2 mode. '0': compare match 1 event generation disabled when counting up '1': compare match 1 event generation enabled when counting up This field has a function in PWM and PWM_DT modes only.
7	CC1_MATCH_DOWN_EN	RW	RW	1	Enables / disables the compare match 1 event generation (COUNTER equals CC0 register) when counting down (STATUS.DOWN = 1) in CNT_UPDN1/2 mode. '0': compare match 1 event generation disabled when counting down '1': compare match 1 event generation enabled when counting down This field has a function in PWM and PWM_DT modes only.
8	PWM_IMM_KILL	RW	RW	0	Specifies whether the kill event immediately deactivates the 'dt_line_out' and 'dt_line_compl_out' signals or with the next module clock ('active count' pre-scaled 'clk_counter'). '0': synchronous kill activation. Deactivates the 'dt_line_out' and 'dt_line_compl_out' signals with the next module clock ('active count' pre-scaled 'clk_counter'). '1': immediate kill activation. Immediately deactivates the 'dt_line_out' and 'dt_line_compl_out' signals. This field has a function in PWM, PWM_DT and PWM_PR modes only.
9	PWM_STOP_ON_KILL	RW	RW	0	Specifies whether the counter stops on a kill events: '0': kill event does NOT stop counter. '1': kill event stops counter. This field has a function in PWM, PWM_DT and PWM_PR modes only.
10	PWM_SYNC_KILL	RW	RW	0	Specifies asynchronous/synchronous kill behavior: '1': synchronous kill mode: the kill event disables the 'dt_line_out' and 'dt_line_compl_out' signals till the next terminal count event (synchronous kill). In synchronous kill mode, STOP_EDGE should be RISING_EDGE. '0': asynchronous kill mode: the kill event only disables the 'dt_line_out' and 'dt_line_compl_out' signals when present. In asynchronous kill mode, STOP_EDGE should be NO_EDGE_DET. This field has a function in PWM and PWM_DT modes only. This field is only used when PWM_STOP_ON_KILL is '0'.
12:13	PWM_DISABLE_MODE	RW	RW	0	Specifies the behavior of the PWM outputs 'line_out' and 'line_compl_out' while the TCPWM counter is disabled (CTL.ENABLED='0') or stopped. Note: The output signal of this selection can be further modified by the immediate kill logic and line_out polarity settings (CTRL.QUAD_ENCODING_MODE).

Bits	Name	SW	HW	Default or Enum	Description
	Z			0	The behavior is the same as in previous mxcpwm (version 1). When the counter is disabled the PWM outputs 'line_out' and 'line_compl_out' are NOT driven by the TCPWM. Instead the port default level configuration applies, e.g. 'Z' (high impedance). Note: This is realized by driving the TCPWM output 'line_out_en' to 0. When the counter is stopped upon a stop event the PWM outputs are deactivated (to the polarity defined by CTL.QUAD_ENCODING_MODE).
	RETAIN			1	When the counter is disabled the PWM outputs 'line_out' and 'line_compl_out' are driven by the TCPWM. When the counter is disabled or stopped upon a stop event the PWM outputs are retained (keep their previous levels). While the counter is disabled or stopped the PWM outputs can be changed via LINE_SEL (when parameter GRP_SMC_PRESENT = 1).
	L			2	When the counter is disabled the PWM outputs 'line_out' and 'line_compl_out' are driven by the TCPWM. When the counter is disabled or stopped upon a stop event the PWM output 'line_out' is driven as a fixed '0' and the PWM output 'line_compl_out' is driven as a fixed '1'.
	H			3	When the counter is disabled the PWM outputs 'line_out' and 'line_compl_out' are driven by the TCPWM. When the counter is disabled or stopped upon a stop event the PWM output 'line_out' is driven as a fixed '1' and the PWM output 'line_compl_out' is driven as a fixed '0'.
16:17	UP_DOWN_MODE	RW	RW	0	Determines counter direction. In QUAD mode this field acts as QUAD_RANGE_MODE field selecting between different counter range, reload value and compare / capture behavior.
	COUNT_UP			0	Count up (to PERIOD). An overflow event is generated when the counter changes from a state in which COUNTER equals PERIOD. A terminal count event is generated when the counter changes from a state in which COUNTER equals PERIOD.
	COUNT_DOWN			1	Count down (to '0'). An underflow event is generated when the counter changes from a state in which COUNTER equals '0'. A terminal count event is generated when the counter changes from a state in which COUNTER equals '0'.
	COUNT_UPDN1			2	Count up (to PERIOD), then count down (to '0'). An overflow event is generated when the counter changes from a state in which COUNTER equals PERIOD. An underflow event is generated when the counter changes from a state in which COUNTER equals '0'. A terminal count event is generated when the counter changes from a state in which COUNTER equals '0'.

Bits	Name	SW	HW	Default or Enum	Description
	COUNT_UPDN2			3	Count up (to PERIOD), then count down (to '0'). An overflow event is generated when the counter changes from a state in which COUNTER equals PERIOD. An underflow event is generated when the counter changes from a state in which COUNTER equals '0'. A terminal count event is generated when the counter changes from a state in which COUNTER equals '0' AND when the counter changes from a state in which COUNTER equals PERIOD (this counter direction can be used for PWM functionality with asymmetrical updates).
	QUAD_RANGE0			0	In QUAD mode this setting selects the QUAD_RANGE0 mode with the following behavior: - COUNTER range is between 0x0000 and 0xFFFF / 0xFFFFFFFF (for GRP_CNT_WIDTH = 16 / 32) - on reload / index event: - CC0 is copied to CC0_BUFF - COUNTER is copied to CC0 - COUNTER is set to midpoint (0x8000 / 0x80000000) - tc and cc0_match events are generated - when COUNTER is 0x0000 or 0xFFFF / 0xFFFFFFFF: - CC0 is copied to CC0_BUFF - COUNTER (0x0000 or 0xFFFF / 0xFFFFFFFF) is copied to CC0 - COUNTER is set to midpoint (0x8000 / 0x80000000) - cc0_match event is generated This mode is 100 percent backward compatible with previous TCPWM quadrature behavior.
	QUAD_RANGE0_CMP			1	In QUAD mode this setting selects the QUAD_RANGE0_CMP mode with the following behavior: - COUNTER range is between 0x0000 and 0xFFFF / 0xFFFFFFFF (for GRP_CNT_WIDTH = 16 / 32) - the capture0 event acts as 2nd reload / index event - on reload / index event: - COUNTER is set to midpoint (0x8000 / 0x80000000) - when 'capture on index' is selected (AUTO_RELOAD_PERIOD=0): - tc event is generated - PERIOD is copied to PERIOD_BUFF - COUNTER is copied to PERIOD - when COUNTER is 0x0000 or 0xFFFF / 0xFFFFFFFF: - COUNTER is set to midpoint (0x8000 / 0x80000000) - when 'capture on wrap-around' is selected (AUTO_RELOAD_PERIOD=1): - tc event is generated - PERIOD is copied to PERIOD_BUFF - COUNTER (0x0000 or 0xFFFF / 0xFFFFFFFF) is copied to PERIOD - 1 or 2 compare functions (depending on CC1_PRESENT) available This mode is to a certain extend backward compatible with previous TCPWM quadrature behavior but allows a compare function during quadrature decoding using the CC0/CC_BUFF registers and the cc0_match event. Because of that the PERIOD/PERIOD_BUFF registers are used instead of CC0/CC_BUFF registers to capture COUNTER at reload / index event or wrap-around.

Bits	Name	SW	HW	Default or Enum	Description
	QUAD_RANGE1_CAPT			2	In QUAD mode this setting selects the QUAD_RANGE1_CAPT mode with the following behavior: - COUNTER range is between 0x0000 and PERIOD - on reload / index event: - COUNTER is set to 0x0000 - tc event is generated - when COUNTER is 0x0000 and decrementing: - COUNTER is set to PERIOD - tc event is generated - when COUNTER equals PERIOD and is incrementing: - COUNTER is set to 0x0000 - tc event is generated - 1 or 2 capture functions (depending on CC1_PRESENT) available - on capture0 / capture1 event: - CC0 / CC1 is copied to CC0_BUFF / CC1_BUFF - COUNTER value is copied to CC0 This mode is NOT backward compatible with previous TCPWM quadrature behavior. It is to a certain extend compatible with previous Traveo 1 QPRC behavior. It allows that the COUNTER register reflects the current angle position of the rotary encoder, i.e. no MOD or SUB calculations need to be done in SW on the COUNTER value to get the current angle position. This allows a DMA copy of the angle position from the COUNTER register. However, a disadvantage of this mode is that fast sequences of tc interrupts can occur (when encoder moves back and forth around start position). It is recommended to not use the tc interrupt in this mode.
	QUAD_RANGE1_CMP			3	In QUAD mode this setting selects the QUAD_RANGE1_CMP mode. The behavior is the same as for QUAD_RANGE1_CAPT mode described above with the only difference that 1 or 2 compare functions (depending on CC1_PRESENT) are available instead of 1 or 2 capture functions.
18	ONE_SHOT	RW	RW	0	When '0', counter runs continuous. When '1', counter is turned off by hardware when a terminal count event is generated.
20:21	QUAD_ENCODING_MODE	RW	RW	0	In QUAD mode this field selects the quadrature encoding mode (X1/X2/X4) or the Up / Down rotary counting mode. In PWM, PWM_DT and PWM_PR modes, these two bits can be used to invert 'dt_line_out' and 'dt_line_compl_out'. Inversion is the last step in generation of 'dt_line_out' and 'dt_line_compl_out'; i.e. a disabled output line 'dt_line_out' has the value QUAD_ENCODING_MODE[0] and a disabled output line 'dt_line_compl_out' has the value QUAD_ENCODING_MODE[1].
	X1			0	X1 encoding (QUAD mode) This encoding is identical with an up / down counting functionality of the following way: Rising edges of input phiA increment or decrement the counter depending on the state of input phiB (direction input).
	X2			1	X2 encoding (QUAD mode)
	X4			2	X4 encoding (QUAD mode)

Bits	Name	SW	HW	Default or Enum	Description
	UP_DOWN			3	Up / Down rotary counting mode. Input phiA increments the counter, input phiB decrements the counter. The trigger edge detection settings apply.
	INV_OUT			1	When bit 0 is '1', QUADRATURE_ENCODING_MODE[0] inverts 'dt_line_out' (PWM/PWM_DT modes)
	INV_COMPL_OUT			2	When bit 1 is '1', QUADRATURE_ENCODING_MODE[1] inverts 'dt_line_compl_out' (PWM/PWM_DT modes)
24:26	MODE	RW	RW	0	Counter mode.
	TIMER			0	Timer mode
	Reserved1			1	N/A
	CAPTURE			2	Capture mode
	QUAD			3	Quadrature mode Different encoding modes can be selected by QUAD_ENCODING_MODE including up/down count functionality. Different counter range, reload value and capture behavior can be selected by QUAD_RANGE_MODE (overloaded field UP_DOWN_MODE).
	PWM			4	Pulse width modulation (PWM) mode
	PWM_DT			5	PWM with deadtime insertion mode
	PWM_PR			6	Pseudo random pulse width modulation
	SR			7	Shift register mode.
30	DBG_FREEZE_EN	RW	RW	0	Specifies the counter behavior in debug mode. '0': The counter operation continues in debug mode. '1': The counter operation freezes in debug mode.
31	ENABLED	RW	RW	0	Counter enable. '0': counter disabled. '1': counter enabled. Counter static configuration information (e.g. CTRL.MODE, all TR_IN_SEL, TR_IN_EDGE_SEL, TR_PWM_CTRL and TR_OUT_SEL register fields) should only be modified when the counter is disabled. When a counter is disabled, command and status information associated to the counter is cleared by HW, this includes: - the associated counter triggers in the CMD register are set to '0'. - the counter's interrupt cause fields in counter's INTR register. - the counter's status fields in counter's STATUS register.. - the counter's trigger outputs ('tr_out0' and tr_out1'). - the counter's line outputs ('line_out' and 'line_compl_out').

31.4.1.1.2 TCPWM_GRP_CNT_STATUS

Description: Counter status register

Address: 0x40580004

Offset: 0x4

Retention: Not Retained

IsDeepSleep: No

Comment: When the counter is disabled (CTRL.ENABLED = 0), then the STATUS.TR_* bit fields are typically reset to their default values. However, there are exceptions possible in the following cases, based on the selected input trigger via TR_IN_SEL*._SEL:

- If a constant '0' is selected, then a '0' is read.
- If a constant '1' is selected, then a '1' is read.
- If a general purpose trigger input 'tr_all_cnt_in' is selected which is also selected by another counter and that counter is enabled, then the actual level of the selected trigger is read.

Default: 0x20

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	TR_STOP [7:7]	TR_RELOAD [6:6]	TR_COUNT [5:5]	TR_CAPTURE0 [4:4]	None [3:1]			DOWN [0:0]

Bits	15	14	13	12	11	10	9	8
Name	RUNNING [15:15]	None [14:12]			LINE_COMPL_OUT [11:11]	LINE_OUT [10:10]	TR_CAPTURE1 [9:9]	TR_START [8:8]

Bits	23	22	21	20	19	18	17	16
Name	DT_CNT_L [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DT_CNT_H [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	DOWN	R	R	0	When '0', counter is counting up. When '1', counter is counting down. In QUAD mode, this field indicates the direction of the latest counter change: '0' when last incremented and '1' when last decremented.
4	TR_CAPTURE0	R	R	0	Indicates the actual level of the selected capture 0 trigger.
5	TR_COUNT	R	R	1	Indicates the actual level of the selected count trigger.
6	TR_RELOAD	R	R	0	Indicates the actual level of the selected reload trigger.
7	TR_STOP	R	R	0	Indicates the actual level of the selected stop trigger.
8	TR_START	R	R	0	Indicates the actual level of the selected start trigger.
9	TR_CAPTURE1	R	R	0	Indicates the actual level of the selected capture 1 trigger.
10	LINE_OUT	R	R	0	Indicates the actual level of the PWM line output signal.
11	LINE_COMPL_OUT	R	R	0	Indicates the actual level of the complementary PWM line output signal.

Bits	Name	SW	HW	Default or Enum	Description
15	RUNNING	R	R	0	When '0', the counter is NOT running. When '1', the counter is running. This field is used to indicate that the counter is running after a start/reload event and that the counter is stopped after a stop event. When a running counter operation is paused in debug state (see CTRL.DBG_PAUSE) then the RUNNING bit is still '1'.
16:23	DT_CNT_L	R	R	0	Generic 8-bit counter field. In PWM_DT mode, this counter is used for dead time insertion (8bit dead time counter or low byte of 16-bit dead time counter). In all other modes, this counter is used for pre-scaling the selected counter clock. PWM_DT mode can NOT use prescaled clock functionality.
24:31	DT_CNT_H	R	R	0	High byte of 16-bit dead time counter. In PWM_DT mode, this counter is used for dead time insertion. In all other modes, this field has no effect. Note: This field only exists when parameter GRP_AMC_PRESENT for advanced motor control is set to 1. Otherwise the dead time is only 8bit wide and the only the field DT_CNT_L is used as dead time counter.

31.4.1.1.3 TCPWM_GRP_CNT_COUNTER

Description: Counter count register
Address: 0x40580008
Offset: 0x8
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	COUNTER [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNTER [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	COUNTER [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	COUNTER [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	COUNTER	RW	RW	0	16-bit / 32-bit counter value. It is advised to not write to this field when the counter is running.

31.4.1.1.4 TCPWM_GRP_CNT_CC0

Description: Counter compare/capture 0 register
Address: 0x40580010
Offset: 0x10
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CC	RW	RW	4294967295	In CAPTURE mode, captures the counter value. In other modes, compared to counter value.

31.4.1.1.5 TCPWM_GRP_CNT_CC0_BUFF

Description: Counter buffered compare/capture 0 register
Address: 0x40580014
Offset: 0x14
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CC	RW	RW	4294967295	Additional buffer for counter CC register.

31.4.1.1.6 TCPWM_GRP_CNT_CC1

Description: Counter compare/capture 1 register
Address: 0x40580018
Offset: 0x18
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CC	RW	RW	4294967295	In CAPTURE mode, captures the counter value. In other modes, compared to counter value.

31.4.1.1.7 TCPWM_GRP_CNT_CC1_BUFF

Description: Counter buffered compare/capture 1 register
Address: 0x4058001C
Offset: 0x1C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CC [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	CC [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	CC [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	CC	RW	RW	4294967295	Additional buffer for counter CC1 register.

31.4.1.1.8 TCPWM_GRP_CNT_PERIOD

Description: Counter period register
Address: 0x40580020
Offset: 0x20
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PERIOD [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PERIOD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	PERIOD	RW	RW	4294967295	Period value: upper value of the counter. When the counter should count for n cycles, this field should be set to n-1.

31.4.1.1.9 TCPWM_GRP_CNT_PERIOD_BUFF

Description: Counter buffered period register
Address: 0x40580024
Offset: 0x24
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0xFFFFFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	PERIOD [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	PERIOD [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	PERIOD [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	PERIOD [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:31	PERIOD	RW	RW	4294967295	Additional buffer for counter PERIOD register. In PWM_PR mode PERIOD_BUFF defines the LFSR polynomial. Each bit represents a tap of the shift register which can be feed back to the MSB via an XOR tree. Examples for GRP_CNT_WIDTH = 16: - Maximum length 16bit LFSR - polynomial $x^{16} + x^{14} + x^{13} + x^{11} + 1$ - taps 0,2,3,5 -> PERIOD = 0x002d - period is $2^{16}-1 = 65535$ cycles - Maximum length 8bit LFSR: - polynomial $x^8 + x^6 + x^5 + x^4 + 1$ - taps 8,10,11,12 (realized in 8 MSBs of 16bit LFSR) - period is $2^8-1 = 255$ cycles In SR mode PERIOD_BUFF defines which tap of the shift register generates the PWM output signals. For a delay of n cycles (from capture event to PWM output) the bit CNT_WIDTH-n should be set to '1'. For a shift register function only one tap should be use, i.e. a one-hot value must be written to PERIOD_BUFF. If multiple bits in PERIOD_BUFF are set then the taps are XOR combined.

31.4.1.1.10 TCPWM_GRP_CNT_LINE_SEL

Description: Counter line selection register
Address: 0x40580028
Offset: 0x28
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x32

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	COMPL_OUT_SEL [6:4]			None [3:3]	OUT_SEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	OUT_SEL	RW	RW	2	Selects the source for the output signal 'line_out'. Default setting is the PWM signal 'line'. Other settings are useful for Stepper Motor Control. This field has a function in PWM and PWM_PR modes only. Note: The output signal of this selection can be further modified by the stop / kill logic and line_out polarity setting (CTRL.QUAD_ENCODING_MODE[0]).
	L			0	fixed '0'
	H			1	fixed '1'
	PWM			2	PWM signal 'line'
	PWM_INV			3	inverted PWM signal 'line'
	Z			4	The output 'line_out' is not driven by the TCPWM. Instead the port default level configuration applies, e.g. 'Z' (high impedance). Note: This is realized by driving the output 'line_out_en' to 0.
	Reserved5			5	N/A
	Reserved6			6	N/A
	Reserved7			7	N/A
4:6	COMPL_OUT_SEL	RW	RW	3	Selects the source for the output signal 'line_compl_out'. Default setting is the inverted PWM signal 'line'. Other settings are useful for Stepper Motor Control. This field has a function in PWM and PWM_PR modes only. Note: The output signal of this selection can be further modified by the stop / kill logic and line_compl_out polarity setting (CTRL.QUAD_ENCODING_MODE[1]).
	L			0	fixed '0'
	H			1	fixed '1'

Bits	Name	SW	HW	Default or Enum	Description
	PWM			2	PWM signal 'line'
	PWM_INV			3	inverted PWM signal 'line'
	Z			4	The output 'line_compl_out' is not driven by the TCPWM. Instead the port default level configuration applies, e.g. 'Z' (high impedance). Note: This is realized by driving the output 'line_compl_out_en' to 0.
	Reserved5			5	N/A
	Reserved6			6	N/A
	Reserved7			7	N/A

31.4.1.1.11 TCPWM_GRP_CNT_LINE_SEL_BUFF

Description: Counter buffered line selection register
Address: 0x4058002C
Offset: 0x2C
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x32

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	COMPL_OUT_SEL [6:4]			None [3:3]	OUT_SEL [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	OUT_SEL	RW	RW	2	Buffer for LINE_SEL.OUT_SEL. Can be exchanged with LINE_SEL.LINE_OUT_SEL on a terminal count event with an actively pending switch event. This field has a function in PWM and PWM_PR modes only.
4:6	COMPL_OUT_SEL	RW	RW	3	Buffer for LINE_SEL.COMPL.OUT_SEL. Can be exchanged with LINE_SEL.LINE_COMPL_OUT_SEL on a terminal count event with an actively pending switch event. This field has a function in PWM and PWM_PR modes only.

31.4.1.1.12 TCPWM_GRP_CNT_DT

Description: Counter PWM dead time register
Address: 0x40580030
Offset: 0x30
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	DT_LINE_OUT_L [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	DT_LINE_OUT_H [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	DT_LINE_COMPL_OUT [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	DT_LINE_COMPL_OUT [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	DT_LINE_OUT_L	RW	RW	0	In PWM_DT mode, this field is used to determine the low byte of the dead time before activating the PWM line output signal 'line_out': amount of dead time cycles in the counter clock domain. In all other modes, the lower 3 bits of this field determine pre-scaling of the selected counter clock. Note: This field determines the low byte of the 16-bit dead time before activating 'line_out' when parameter GRP_AMC_PRESENT for advanced motor control is set to 1. Otherwise the dead time is only 8 bit wide and the same dead time specified by this DT_LINE_OUT_L field is used before activating 'line_out' and 'line_compl_out'.
	DIVBY1			0	Divide by 1 (other-than-PWM_DT mode)
	DIVBY2			1	Divide by 2 (other-than-PWM_DT mode)
	DIVBY4			2	Divide by 4 (other-than-PWM_DT mode)
	DIVBY8			3	Divide by 8 (other-than-PWM_DT mode)
	DIVBY16			4	Divide by 16 (other-than-PWM_DT mode)
	DIVBY32			5	Divide by 32 (other-than-PWM_DT mode)
	DIVBY64			6	Divide by 64 (other-than-PWM_DT mode)
	DIVBY128			7	Divide by 128 (other-than-PWM_DT mode)
8:15	DT_LINE_OUT_H	RW	RW	0	In PWM_DT mode, this field is used to determine the high byte of the dead time before activating the PWM line output signal 'line_out': amount of dead time cycles in the counter clock domain. In all other modes, this field has no effect. Note: This field only exists when parameter GRP_AMC_PRESENT for advanced motor control is set to 1. Otherwise the dead time is only 8 bit wide and the same dead time specified by field DT_LINE_OUT_L is used before activating 'line_out' and 'line_compl_out'.

Bits	Name	SW	HW	Default or Enum	Description
16:31	DT_LINE_COMPL_OUT	RW	RW	0	In PWM_DT mode, this field is used to determine the dead time before activating the complementary PWM line output signal 'line_compl_out': amount of dead time cycles in the counter clock domain. In all other modes, this field has no effect. Note: This field only exists when parameter GRP_AMC_PRESENT for advanced motor control is set to 1. Otherwise the dead time is only 8 bit wide and the same dead time specified by field DT_LINE_OUT_L is used before activating 'line_out' and 'line_compl_out'.

31.4.1.1.13 TCPWM_GRP_CNT_TR_CMD

Description: Counter trigger command register
Address: 0x40580040
Offset: 0x40
Retention: Not Retained
IsDeepSleep: No
Comment: Enables software controlled operation for this counter.
 Note: Synchronized operation on multiple counters can be done using trigger multipliers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:6]		CAPTURE1 [5:5]	START [4:4]	STOP [3:3]	RELOAD [2:2]	None [1:1]	CAPTURE0 [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	CAPTURE0	RW1S	RW1S	0	SW capture 0 trigger. When written with '1', a capture 0 trigger is generated and the HW sets the field to '0' when the SW trigger has taken effect. It should be noted that the HW operates on the counter frequency. If the counter is disabled through CTRL.ENABLED, the field is immediately set to '0'.
2	RELOAD	RW1S	RW1S	0	SW reload trigger. For HW behavior, see COUNTER_CAPTURE0 field.
3	STOP	RW1S	RW1S	0	SW stop trigger. For HW behavior, see COUNTER_CAPTURE0 field.
4	START	RW1S	RW1S	0	SW start trigger. For HW behavior, see COUNTER_CAPTURE0 field.
5	CAPTURE1	RW1S	RW1S	0	SW capture 1 trigger. For HW behavior, see COUNTER_CAPTURE0 field.

31.4.1.1.14 TCPWM_GRP_CNT_TR_IN_SEL0

Description: Counter input trigger selection register 0
Address: 0x40580044
Offset: 0x44
Retention: Retained
IsDeepSleep: No
Comment: Used to select triggers for specific counter events.
Default: 0x100

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CAPTURE0_SEL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	COUNT_SEL [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	RELOAD_SEL [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	STOP_SEL [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	CAPTURE0_SEL	RW	RW	0	Selects one of the up to 256 input triggers as a capture0 trigger. Input trigger 0 is always '0' and input trigger 1 is always '1'. If existing, the one-to-one trigger inputs 'tr_one_cnt_in' (different to each counter) are selected by setting 2 and above. The settings above are used for the general purpose trigger inputs 'tr_all_cnt_in' connected to all counters selected. In the PWM, PWM_DT and PWM_PR modes this trigger is used to switch the values if the compare and period registers with their buffer counterparts.
8:15	COUNT_SEL	RW	RW	1	Selects one of the 256 input triggers as a count trigger. In QUAD mode, this is the first phase (phi A). Default setting selects input trigger 1, which is always '1'. Note: In the modes: TIMER, CAPTURE, PWM, PWM_DT, and SR, If the counter is externally triggered (COUNT_SEL > 1), an external trigger will be required for each TR_CMD to execute. For example, a write to TR_CMD.START will not start the counter until the trigger selected by COUNT_SEL asserts. The next trigger will increment the counter since the counter is now running. This goes for all TR_CMD fields.
16:23	RELOAD_SEL	RW	RW	0	Selects one of the 256 input triggers as a reload trigger. In QUAD mode, this is the index or revolution pulse. In these modes, it will update the counter with 0x8000 (counter midpoint) or 0x0000 depending on the QUAD_RANGE_MODE.

Bits	Name	SW	HW	Default or Enum	Description
24:31	STOP_SEL	RW	RW	0	Selects one of the 256 input triggers as a stop trigger. In PWM, PWM_DT and PWM_PR modes, this is the kill trigger. In these modes, the kill trigger is used to either temporarily block the PWM outputs (PWM_STOP_ON_KILL is '0') or stop the functionality (PWM_STOP_ON_KILL is '1'). For the PWM and PWM_DT modes, the blocking of the output signals can be asynchronous (STOP_EDGE should be NO_EDGE_DET) in which case the blocking is as long as the trigger is '1' or synchronous (STOP_EDGE should be RISING_EDGE) in which case it extends till the next terminal count event.

31.4.1.1.15 TCPWM_GRP_CNT_TR_IN_SEL1

Description: Counter input trigger selection register 1
Address: 0x40580048
Offset: 0x48
Retention: Retained
IsDeepSleep: No
Comment: Used to select triggers for specific counter events.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	START_SEL [7:0]							

Bits	15	14	13	12	11	10	9	8
Name	CAPTURE1_SEL [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:7	START_SEL	RW	RW	0	Selects one of the 256 input triggers as a start trigger. In QUAD mode, this is the second phase (phi B).
8:15	CAPTURE1_SEL	RW	RW	0	Selects one of the 256 input triggers as a capture 1 trigger.

31.4.1.1.16 TCPWM_GRP_CNT_TR_IN_EDGE_SEL

Description: Counter input trigger edge selection register
Address: 0x4058004C
Offset: 0x4C
Retention: Retained
IsDeepSleep: No
Comment: Used to determine edge detection for specific counter triggers. Events will only take effect on enabled counters.
Default: 0xFFFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	STOP_EDGE [7:6]		RELOAD_EDGE [5:4]		COUNT_EDGE [3:2]		CAPTURE0_EDGE [1:0]	
Bits	15	14	13	12	11	10	9	8
Name	None [15:12]				CAPTURE1_EDGE [11:10]		START_EDGE [9:8]	
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	CAPTURE0_EDGE	RW	RW	3	A capture 0 event will copy the counter value into the CC0 register.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.
2:3	COUNT_EDGE	RW	RW	3	A counter event will increase or decrease the counter by '1'.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.
4:5	RELOAD_EDGE	RW	RW	3	A reload event will initialize the counter. When counting up, the counter is initialized to '0'. When counting down, the counter is initialized with PERIOD.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.
6:7	STOP_EDGE	RW	RW	3	A stop event, will stop the counter; i.e. it will no longer be running. Stopping will NOT disable the counter.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.

Bits	Name	SW	HW	Default or Enum	Description
8:9	START_EDGE	RW	RW	3	A start event will start the counter; i.e. the counter will become running. Starting does NOT enable the counter. A start event will not initialize the counter whereas the reload event does.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.
10:11	CAPTURE1_EDGE	RW	RW	3	A capture 1 event will copy the counter value into the CC1 register.
	RISING_EDGE			0	Rising edge. Any rising edge generates an event.
	FALLING_EDGE			1	Falling edge. Any falling edge generates an event.
	ANY_EDGE			2	Rising AND falling edge. Any odd amount of edges generates an event.
	NO_EDGE_DET			3	No edge detection, use trigger as is.

31.4.1.1.17 TCPWM_GRP_CNT_TR_PWM_CTRL

Description: Counter trigger PWM control register
Address: 0x40580050
Offset: 0x50
Retention: Retained
IsDeepSleep: No
Comment: Used to control counter 'line_out', 'dt_line_out' and 'dt_line_compl_out' output signals.
Default: 0xFF

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	CC1_MATCH_MODE [7:6]		UNDERFLOW_MODE [5:4]		OVERFLOW_MODE [3:2]		CC0_MATCH_MODE [1:0]	
Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							
Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							
Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:1	CC0_MATCH_MODE	RW	RW	3	Determines the effect of a compare match 0 event (COUNTER equals CC0 register) on the 'line_out' output signals. Note that INVERT is especially useful for center aligned pulse width modulation. To generate a duty cycle of 0 percent, the counter CC0 register should be set to '0'. For a 100 percent duty cycle, the counter CC0 register should be set to larger than the counter PERIOD register.
	SET			0	Set to '1'
	CLEAR			1	Set to '0'
	INVERT			2	Invert
	NO_CHANGE			3	No Change
2:3	OVERFLOW_MODE	RW	RW	3	Determines the effect of a counter overflow event (COUNTER reaches PERIOD) on the 'line_out' output signals.
	SET			0	Set to '1'
	CLEAR			1	Set to '0'
	INVERT			2	Invert
	NO_CHANGE			3	No Change
4:5	UNDERFLOW_MODE	RW	RW	3	Determines the effect of a counter underflow event (COUNTER reaches '0') on the 'line_out' output signals.
	SET			0	Set to '1'
	CLEAR			1	Set to '0'
	INVERT			2	Invert
	NO_CHANGE			3	No Change
6:7	CC1_MATCH_MODE	RW	RW	3	Determines the effect of a compare match 1 event (COUNTER equals CC1 register) on the 'line_out' output signals.
	SET			0	Set to '1'
	CLEAR			1	Set to '0'
	INVERT			2	Invert

Bits	Name	SW	HW	Default or Enum	Description
	NO_CHANGE			3	No Change

31.4.1.1.18 TCPWM_GRP_CNT_TR_OUT_SEL

Description: Counter output trigger selection register
Address: 0x40580054
Offset: 0x54
Retention: Retained
IsDeepSleep: No
Comment: Used to select internal events for output trigger generation.
Default: 0x32

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:7]	OUT1 [6:4]			None [3:3]	OUT0 [2:0]		

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0:2	OUT0	RW	RW	2	Selects one of the internal events to generate the output trigger 0. Default setting selects the terminal count event.
	OVERFLOW			0	Overflow event
	UNDERFLOW			1	Underflow event
	TC			2	Terminal count event (default selection)
	CC0_MATCH			3	Compare match 0 event
	CC1_MATCH			4	Compare match 1 event
	LINE_OUT			5	PWM output signal 'line_out'
	Reserved6			6	N/A
4:6	OUT1	RW	RW	3	Selects one of the internal events to generate the output trigger 1. Default setting selects the compare match 0 event.
	OVERFLOW			0	Overflow event
	UNDERFLOW			1	Underflow event
	TC			2	Terminal count event
	CC0_MATCH			3	Compare match 0 event (default selection)
	CC1_MATCH			4	Compare match 1 event
	LINE_OUT			5	PWM output signal 'line_out'
	Reserved6			6	N/A
	Disabled			7	Output trigger disabled.

31.4.1.1.19 TCPWM_GRP_CNT_INTR

Description: Interrupt request register
Address: 0x40580070
Offset: 0x70
Retention: Not Retained
IsDeepSleep: No
Comment: The register fields are not retained. This is to ensure that they come up as '0' after coming out of DeepSleep system power mode. HW clears the interrupt causes to '0', when the counter is disabled.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CC1_MATCH [2:2]	CC0_MATCH [1:1]	TC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TC	RW1C	RW1C	0	Terminal count event. Set to '1', when event is detected. Write with '1' to clear bit.
1	CC0_MATCH	RW1C	RW1C	0	Counter matches CC0 register event. Set to '1', when event is detected. Write with '1' to clear bit.
2	CC1_MATCH	RW1C	RW1C	0	Counter matches CC1 register event. Set to '1', when event is detected. Write with '1' to clear bit.

31.4.1.1.20 TCPWM_GRP_CNT_INTR_SET

Description: Interrupt set request register
Address: 0x40580074
Offset: 0x74
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects the interrupt request register.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CC1_MATCH [2:2]	CC0_MATCH [1:1]	TC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TC	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
1	CC0_MATCH	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.
2	CC1_MATCH	RW1S	RW1S	0	Write with '1' to set corresponding bit in interrupt request register.

31.4.1.1.21 TCPWM_GRP_CNT_INTR_MASK

Description: Interrupt mask register
Address: 0x40580078
Offset: 0x78
Retention: Retained
IsDeepSleep: No
Comment:
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CC1_MATCH [2:2]	CC0_MATCH [1:1]	TC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TC	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
1	CC0_MATCH	RW	RW	0	Mask bit for corresponding bit in interrupt request register.
2	CC1_MATCH	RW	RW	0	Mask bit for corresponding bit in interrupt request register.

31.4.1.1.22 TCPWM_GRP_CNT_INTR_MASKED

Description: Interrupt masked request register
Address: 0x4058007C
Offset: 0x7C
Retention: Not Retained
IsDeepSleep: No
Comment: When read, this register reflects a bitwise AND between the interrupt request and mask registers.
Default: 0x0

Bit-field Table

Bits	7	6	5	4	3	2	1	0
Name	None [7:3]					CC1_MATCH [2:2]	CC0_MATCH [1:1]	TC [0:0]

Bits	15	14	13	12	11	10	9	8
Name	None [15:8]							

Bits	23	22	21	20	19	18	17	16
Name	None [23:16]							

Bits	31	30	29	28	27	26	25	24
Name	None [31:24]							

Bit-fields

Bits	Name	SW	HW	Default or Enum	Description
0	TC	R	R	0	Logical and of corresponding request and mask bits.
1	CC0_MATCH	R	R	0	Logical and of corresponding request and mask bits.
2	CC1_MATCH	R	R	0	Logical and of corresponding request and mask bits.

References

References

- [1] 002-33816: XMC7000 family Architecture technical reference manual (TRM)

Revision history

Revision history

Document version	Date of release	Description of changes
**	2021-10-22	Initial release

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-10-22

Published by

**Infineon Technologies AG
81726 Munich, Germany**

**© 2021 Infineon Technologies AG.
All Rights Reserved.**

**Do you have a question about any
aspect of this document?**

Go to www.cypress.com/support

Document reference

002-33817 Rev. **

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.